

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012065

Luminaire Tested: S123DIP-B775D585UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012065
REPORT IS A COMBINATION OF REPORTS P990452 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-B775D585UB50-4F0-XX-W2A-A4
Description: Define 3 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5196.0 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	101	96	92	89	94	90	87	84	79	76	74	68	67	65	59	58	56
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48
3	84	75	67	61	78	70	64	58	62	57	52	54	50	47	46	44	41
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31
6	65	53	45	39	61	50	43	37	44	39	34	39	34	31	34	31	28
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	27	25
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11241	11241	11241	11241
5°	11248	12953	11282	9666
10°	11177	15673	11189	8442
15°	11023	18588	11113	7598
20°	10889	21401	10913	6992
25°	10693	21940	10716	6675
30°	10552	18127	10552	6468
35°	10377	12123	10311	6284
40°	10166	8751	10041	6004
45°	9904	6932	9619	5655
50°	9264	5887	8936	5313
55°	8563	5173	8215	4931
60°	7851	4504	7435	4530
65°	7071	3856	6728	3995
70°	6258	3201	5840	3369
75°	5352	2414	5006	2599
80°	4229	1612	3898	1709
85°	2920	740	2334	674

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 18129 cd/sqm

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.7	2.0
10°-20°	329.9	6.3
20°-30°	555.1	10.7
30°-40°	627.3	12.1
40°-50°	561.8	10.8
50°-60°	453.5	8.7
60°-70°	316.0	6.1
70°-80°	165.9	3.2
80°-90°	41.3	0.8
90°-100°	147.3	2.8
100°-110°	431.4	8.3
110°-120°	421.3	8.1
120°-130°	335.5	6.5
130°-140°	264.7	5.1
140°-150°	197.5	3.8
150°-160°	137.7	2.6
160°-170°	80.9	1.6
170°-180°	26.3	0.5
0°-30°	987.7	19.0
0°-40°	1615.0	31.1
0°-60°	2630.3	50.6
0°-90°	3153.5	60.7
90°-120°	1000.0	19.2
90°-150°	1797.7	34.6
90°-180°	2043.0	39.3
0°-180°	5196.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1044	1044	1044	1044	1044	
5°	1043	1241	1046	926	1043	99
15°	996	1847	1004	755	996	281
25°	911	2192	913	667	911	420
35°	804	1181	798	612	804	503
45°	667	638	648	520	667	510
55°	473	433	453	413	473	423
65°	292	281	278	291	292	291
75°	141	145	132	156	141	151
85°	30	33	24	30	30	35
90°	1	16	1	16	1	4
95°	19	64	19	64	19	20
105°	64	699	64	699	64	68
115°	113	850	113	850	113	112
125°	157	671	157	671	157	139
135°	184	544	184	544	184	142
145°	209	425	209	425	209	131
155°	238	352	238	352	238	109
165°	260	307	260	307	260	73
175°	271	276	271	276	271	26
180°	272	272	272	272	272	

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1047.4	1055.5	1059.5	1065.6	1071.7	1080.8	1083.8	1088.9	1086.8	1090.9	1092.9
5°	1043.3	1057.5	1069.6	1084.8	1099.0	1109.1	1119.2	1135.4	1147.6	1149.6	1158.7
7.5°	1036.2	1056.5	1077.7	1099.0	1126.3	1142.5	1160.7	1183.0	1201.2	1230.5	1241.7
10°	1027.1	1055.5	1085.8	1115.2	1152.6	1177.9	1200.2	1237.6	1275.1	1305.4	1333.8
12.5°	1013.0	1048.4	1087.9	1131.4	1179.9	1209.3	1239.7	1289.2	1345.9	1392.5	1422.8
15°	995.8	1040.3	1090.9	1137.4	1191.1	1245.7	1278.1	1333.8	1414.7	1458.2	1536.2
17.5°	981.6	1027.1	1077.7	1150.6	1223.5	1278.1	1301.4	1403.6	1459.2	1532.1	1620.2
20°	959.3	1017.0	1081.8	1154.6	1248.8	1282.2	1329.7	1432.9	1501.8	1596.9	1705.2
22.5°	936.1	997.8	1075.7	1151.6	1256.9	1292.3	1357.0	1439.0	1548.3	1642.4	1761.8
25°	910.8	977.6	1056.5	1146.6	1249.8	1301.4	1362.1	1463.3	1581.7	1700.1	1810.4
27.5°	885.5	958.3	1040.3	1130.4	1230.5	1291.3	1352.0	1457.2	1609.0	1737.5	1878.2
30°	861.2	934.0	1016.0	1108.1	1213.3	1272.0	1329.7	1461.3	1630.3	1775.0	1916.7
32.5°	834.9	909.8	995.8	1072.7	1178.9	1241.7	1306.4	1461.3	1643.4	1797.2	1926.8
35°	803.5	880.4	954.3	1031.2	1136.4	1206.3	1279.1	1451.2	1655.6	1804.3	1884.3
37.5°	773.1	840.9	904.7	979.6	1089.9	1164.8	1248.8	1439.0	1649.5	1774.0	1796.2
40°	738.7	806.5	858.1	928.0	1044.3	1131.4	1216.4	1422.8	1623.2	1702.1	1637.4
42.5°	705.3	759.0	803.5	871.3	997.8	1082.8	1174.9	1393.5	1571.6	1587.8	1442.0
45°	666.9	705.3	744.8	821.7	947.2	1034.2	1136.4	1351.0	1488.6	1442.0	1257.9
47.5°	617.3	651.7	695.2	766.1	893.6	983.6	1080.8	1296.3	1368.2	1271.0	1069.6
50°	569.7	599.1	639.6	708.4	836.9	924.9	1028.2	1210.3	1245.7	1092.9	921.9
52.5°	522.2	544.4	583.9	652.7	781.2	866.2	960.4	1122.3	1102.0	938.1	786.3
55°	472.6	491.8	529.3	597.1	716.5	797.4	887.5	1014.0	961.4	805.5	684.1
57.5°	424.0	444.3	482.7	539.4	651.7	730.6	802.5	901.7	822.7	698.3	591.0
60°	380.5	397.7	427.0	482.7	584.9	648.7	714.4	782.2	716.5	596.0	514.1
62.5°	335.0	351.2	378.5	429.1	517.1	573.8	626.4	682.1	609.2	521.2	448.3
65°	292.5	305.6	330.9	377.5	449.3	495.9	538.4	576.8	518.1	437.2	382.5
67.5°	254.0	265.1	286.4	327.9	388.6	422.0	456.4	488.8	439.2	374.4	327.9
70°	212.5	221.6	240.8	271.2	319.8	354.2	379.5	403.8	359.2	307.6	276.3
72.5°	176.1	185.2	197.3	228.7	262.1	283.3	310.7	323.8	298.5	256.0	224.7
75°	140.7	147.7	158.9	179.1	210.5	224.7	241.9	252.0	228.7	200.4	181.1
77.5°	110.3	113.3	121.4	135.6	156.9	173.0	186.2	192.3	176.1	157.9	141.7
80°	77.9	82.0	88.0	100.2	116.4	121.4	129.5	136.6	126.5	110.3	100.2
82.5°	51.6	56.7	59.7	64.8	74.9	81.0	83.0	89.1	79.9	73.9	69.8
85°	30.4	32.4	33.4	36.4	41.5	44.5	47.6	48.6	46.6	45.5	41.5
87.5°	15.2	15.2	15.2	17.2	18.2	20.2	21.3	21.3	21.3	20.2	19.2
90°	1.1	2.2	3.3	4.9	6.0	6.6	7.1	8.8	10.4	12.1	13.7
92.5°	8.2	12.1	17.6	22.5	28.0	33.0	37.9	55.5	84.6	113.2	102.2
95°	18.7	20.3	26.4	35.7	50.0	60.8	71.5	118.2	200.1	290.2	325.9
97.5°	29.7	30.2	35.2	43.4	57.7	69.5	81.3	127.5	222.6	374.3	501.3
100°	40.7	41.2	45.1	52.8	66.0	76.7	87.4	125.9	207.2	351.8	520.5
102.5°	52.2	53.3	56.6	63.8	75.3	84.9	94.5	128.1	194.0	318.8	484.8
105°	63.8	65.4	68.7	75.3	85.7	94.2	102.8	132.5	189.1	293.0	441.9
107.5°	75.9	77.5	80.8	87.4	97.3	105.2	113.2	139.6	188.0	274.3	404.0
110°	89.0	90.7	93.4	99.5	108.8	116.5	124.2	149.0	190.7	264.4	372.7

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	101.1	102.8	105.5	111.6	120.9	128.4	135.8	158.3	196.2	258.9	351.8
115°	112.7	114.9	118.2	123.7	133.0	140.4	147.9	168.7	202.3	258.3	338.0
117.5°	124.2	127.0	129.7	134.7	145.1	152.0	158.9	179.7	210.0	258.9	328.7
120°	136.3	138.0	140.7	146.2	156.7	163.6	170.4	190.2	218.8	261.1	322.7
122.5°	146.8	148.4	151.2	157.2	167.1	174.5	181.9	201.2	227.0	264.9	318.8
125°	156.7	157.8	161.1	167.1	177.5	185.0	192.4	211.6	235.8	268.8	315.5
127.5°	164.3	166.0	169.8	175.9	187.4	194.9	202.3	221.0	243.0	273.2	313.9
130°	171.5	173.1	178.1	184.7	196.2	203.6	211.1	229.2	250.1	277.6	312.2
132.5°	177.0	179.2	184.7	192.9	204.5	211.6	218.8	236.4	256.7	280.9	311.7
135°	183.6	185.8	191.8	200.1	211.6	219.0	226.5	243.5	262.2	284.2	311.1
137.5°	189.6	191.8	197.9	206.7	218.2	225.1	232.0	248.4	266.6	286.4	310.0
140°	195.7	198.4	203.9	212.7	223.7	230.6	237.5	253.4	269.9	288.6	309.5
142.5°	202.3	204.5	210.5	218.2	229.2	235.6	241.9	257.2	273.2	290.2	308.4
145°	209.4	211.1	216.0	224.3	233.6	239.9	246.2	260.5	275.4	290.8	307.3
147.5°	216.6	217.7	222.6	229.8	239.1	244.6	250.1	263.3	277.0	290.8	305.6
150°	223.7	224.3	228.7	235.8	243.5	248.4	253.4	266.0	277.6	290.8	303.4
152.5°	230.9	230.9	235.3	241.3	247.9	252.6	257.2	267.7	278.7	289.1	300.7
155°	238.0	238.0	241.3	246.8	252.8	256.6	260.5	269.9	278.7	288.0	297.4
157.5°	243.5	244.0	246.8	251.7	257.2	260.2	263.3	271.0	279.2	286.4	294.6
160°	250.1	250.1	252.3	256.7	260.5	263.2	266.0	272.6	279.2	285.3	291.3
162.5°	255.0	255.0	256.7	260.0	263.3	265.5	267.7	273.2	278.7	283.1	288.0
165°	260.0	259.4	260.5	263.3	265.5	267.4	269.3	273.7	277.6	280.9	284.7
167.5°	263.8	263.3	263.8	266.0	267.7	269.0	270.4	273.7	277.0	278.7	281.4
170°	267.1	266.0	266.6	268.2	269.3	269.8	270.4	273.2	275.4	276.5	278.1
172.5°	269.3	268.8	268.8	269.9	270.4	270.7	271.0	273.2	274.8	274.8	275.4
175°	271.0	270.4	269.9	271.0	271.0	271.2	271.5	272.6	273.7	273.2	273.2
177.5°	272.1	271.5	271.0	271.5	271.5	271.5	271.5	272.1	273.2	272.1	271.5
180°	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1100.0	1102.0	1109.1	1114.2	1124.3	1123.3	1123.3	1122.3	1119.2	1124.3	1127.3
5°	1176.9	1194.1	1196.1	1218.4	1219.4	1228.5	1234.6	1229.5	1241.7	1240.7	1231.6
7.5°	1272.0	1295.3	1306.4	1327.7	1352.0	1345.9	1369.2	1373.2	1371.2	1381.3	1388.4
10°	1376.3	1416.7	1445.1	1484.5	1494.7	1500.7	1515.9	1529.1	1555.4	1535.1	1548.3
12.5°	1495.7	1525.0	1562.5	1625.2	1656.6	1676.8	1683.9	1693.0	1711.2	1700.1	1701.1
15°	1595.9	1635.3	1699.1	1777.0	1786.1	1811.4	1805.3	1860.0	1886.3	1846.8	1869.1
17.5°	1700.1	1752.7	1828.6	1896.4	1934.9	1952.1	1968.3	2020.9	2018.9	2012.8	2017.9
20°	1766.9	1852.9	1947.0	2037.1	2048.2	2061.4	2104.9	2127.1	2123.1	2140.3	2151.4
22.5°	1861.0	1952.1	2052.3	2112.0	2137.3	2152.4	2186.8	2201.0	2207.1	2211.1	2204.1
25°	1939.9	2037.1	2111.0	2163.6	2178.8	2186.8	2198.0	2202.0	2199.0	2191.9	2198.0
27.5°	1993.6	2071.5	2122.1	2146.4	2138.3	2125.1	2103.9	2089.7	2058.3	2043.2	2061.4
30°	2015.8	2050.2	2065.4	2024.9	1984.5	1952.1	1911.6	1836.7	1778.0	1795.2	1771.9
32.5°	1980.4	1958.1	1885.3	1781.1	1749.7	1697.1	1582.7	1494.7	1497.7	1451.2	1470.4
35°	1876.2	1775.0	1637.4	1479.5	1438.0	1409.7	1284.2	1265.0	1224.5	1181.0	1193.1
37.5°	1692.0	1544.3	1377.3	1260.9	1199.2	1137.4	1066.6	1024.1	999.8	981.6	995.8
40°	1467.3	1287.2	1149.6	1045.4	992.7	953.3	904.7	862.2	834.9	831.8	836.9
42.5°	1246.7	1094.9	968.4	869.3	852.1	805.5	774.2	740.8	732.7	719.5	726.6
45°	1055.5	932.0	827.8	746.8	726.6	714.4	676.0	654.7	645.6	637.5	649.7
47.5°	916.8	787.3	711.4	662.8	642.6	622.4	601.1	586.9	579.9	580.9	579.9
50°	783.3	688.1	621.3	583.9	571.8	557.6	540.4	531.3	528.2	519.1	526.2
52.5°	674.0	605.2	558.6	523.2	514.1	504.0	489.8	484.7	477.6	475.6	475.6
55°	585.9	532.3	494.8	471.6	460.4	452.3	444.3	438.2	433.1	433.1	433.1
57.5°	517.1	470.6	443.2	423.0	419.0	410.9	401.7	401.7	394.7	393.7	396.7
60°	458.4	416.9	395.7	378.5	372.4	370.4	361.3	361.3	359.2	354.2	358.2
62.5°	398.7	368.4	350.1	337.0	330.9	330.9	323.8	318.8	318.8	319.8	317.8
65°	344.1	321.8	305.6	295.5	292.5	288.4	287.4	283.3	280.3	281.3	280.3
67.5°	295.5	278.3	267.2	259.1	254.0	252.0	248.9	248.9	246.9	247.9	242.9
70°	252.0	234.8	225.7	217.6	215.5	215.5	211.5	212.5	210.5	213.5	211.5
72.5°	207.5	194.3	187.2	184.2	182.2	181.1	179.1	177.1	176.1	178.1	177.1
75°	168.0	156.9	151.8	149.8	147.7	147.7	146.7	145.7	144.7	144.7	144.7
77.5°	130.5	123.5	117.4	119.4	116.4	117.4	114.4	114.4	115.4	114.4	114.4
80°	96.1	91.1	91.1	89.1	85.0	87.0	87.0	84.0	83.0	85.0	82.0
82.5°	63.8	62.7	60.7	59.7	57.7	58.7	57.7	56.7	55.7	57.7	55.7
85°	37.4	37.4	36.4	34.4	36.4	35.4	34.4	34.4	33.4	33.4	33.4
87.5°	19.2	17.2	17.2	16.2	17.2	15.2	16.2	15.2	14.2	15.2	14.2
90°	13.2	13.7	14.3	14.8	15.4	15.9	15.4	15.9	16.5	15.9	16.5
92.5°	76.4	54.4	42.3	36.8	34.9	33.0	31.9	29.7	30.2	29.1	30.2
95°	264.4	197.9	134.1	105.0	95.1	85.2	74.8	69.8	66.0	63.8	66.0
97.5°	518.3	454.6	343.0	270.4	239.1	207.8	170.9	150.1	136.9	130.8	136.9
100°	628.8	648.1	603.5	539.2	500.2	461.2	405.7	365.5	344.1	344.6	344.1
102.5°	634.3	712.4	721.7	690.9	669.8	648.6	608.5	578.8	561.8	545.8	561.8
105°	599.7	714.6	769.5	780.0	772.8	765.7	740.4	719.5	701.9	699.2	701.9
107.5°	550.2	681.6	767.9	810.8	818.2	825.6	822.3	812.4	805.3	799.2	805.3
110°	504.0	629.9	731.0	800.3	819.6	838.8	854.2	858.6	857.5	856.4	857.5

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	463.9	578.8	682.7	762.4	788.5	814.6	845.9	861.9	867.4	867.9	867.4
115°	433.1	534.8	630.5	711.3	741.2	771.2	812.4	836.6	847.6	850.3	847.6
117.5°	412.8	500.7	585.4	659.6	690.7	721.7	764.6	791.5	808.0	811.8	808.0
120°	397.4	474.9	549.1	615.1	642.8	670.6	714.0	744.8	758.0	761.3	758.0
122.5°	384.8	454.6	520.0	579.9	605.2	630.5	667.8	694.8	709.6	714.0	709.6
125°	374.3	437.0	496.9	549.7	571.7	593.6	628.8	653.0	666.7	670.6	666.7
127.5°	364.4	421.0	475.5	523.8	544.2	564.5	596.4	617.3	629.9	633.2	629.9
130°	356.7	406.2	455.7	500.2	518.9	537.6	566.7	586.5	598.0	602.4	598.0
132.5°	349.6	392.5	437.0	477.7	495.2	512.8	539.8	559.6	569.4	572.2	569.4
135°	343.5	380.4	419.4	455.1	470.8	486.5	513.4	529.9	539.8	543.6	539.8
137.5°	338.0	368.8	401.8	433.7	447.7	461.7	484.8	501.8	510.1	513.4	510.1
140°	333.1	358.9	387.0	413.3	425.2	437.0	457.9	473.3	482.1	481.5	482.1
142.5°	328.7	349.6	372.7	394.7	404.5	414.4	431.5	444.7	452.4	451.8	452.4
145°	324.8	342.4	360.6	378.2	386.2	394.1	407.8	419.4	423.8	424.9	423.8
147.5°	321.0	336.4	351.2	366.1	371.8	377.6	388.6	396.9	401.3	401.8	401.3
150°	317.2	329.8	342.4	354.0	359.2	364.4	372.7	378.7	382.0	382.0	382.0
152.5°	312.8	323.8	334.2	344.1	348.2	352.3	358.4	363.9	365.5	365.5	365.5
155°	308.4	317.7	326.5	334.7	338.0	341.3	346.3	350.7	351.8	352.3	351.8
157.5°	303.4	311.1	318.8	325.4	328.2	330.9	335.3	338.6	339.7	339.7	339.7
160°	298.5	305.6	311.7	317.2	319.1	321.0	324.8	328.1	328.1	327.6	328.1
162.5°	293.5	299.0	304.0	308.9	310.5	312.2	314.4	317.2	317.2	316.6	317.2
165°	289.1	293.5	296.8	300.7	302.0	303.4	305.6	307.8	307.3	307.3	307.3
167.5°	284.7	288.6	291.3	293.5	294.6	295.7	296.8	298.5	297.9	297.9	297.9
170°	280.9	283.6	285.3	287.5	288.0	288.6	289.1	290.2	289.7	289.7	289.7
172.5°	277.0	279.2	280.3	282.0	282.2	282.5	282.5	283.6	282.5	282.0	282.5
175°	274.3	275.4	275.9	277.0	277.0	277.0	277.0	277.6	277.0	276.5	277.0
177.5°	272.1	272.6	273.2	273.7	273.7	273.7	273.2	273.7	272.6	272.6	272.6
180°	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1119.2	1122.3	1114.2	1112.1	1112.1	1116.2	1113.2	1085.8	1090.9	1084.8	1082.8
5°	1242.7	1236.6	1228.5	1224.5	1219.4	1205.2	1204.2	1172.9	1166.8	1146.6	1137.4
7.5°	1378.3	1373.2	1348.9	1345.9	1343.9	1330.7	1297.3	1263.9	1239.7	1216.4	1194.1
10°	1533.1	1517.9	1506.8	1484.5	1473.4	1455.2	1411.7	1380.3	1338.8	1303.4	1256.9
12.5°	1719.3	1702.1	1664.7	1648.5	1634.3	1583.7	1540.2	1504.8	1423.8	1399.5	1341.9
15°	1855.9	1819.5	1815.5	1780.0	1778.0	1722.4	1639.4	1600.9	1538.2	1449.1	1389.4
17.5°	2003.7	1971.3	1946.0	1903.5	1897.4	1844.8	1784.1	1690.0	1621.2	1536.2	1460.3
20°	2112.0	2094.8	2051.2	2034.0	1998.6	1954.1	1891.4	1775.0	1691.0	1606.0	1512.9
22.5°	2198.0	2180.8	2146.4	2123.1	2102.9	2045.2	1970.3	1871.1	1755.8	1644.4	1548.3
25°	2197.0	2191.9	2177.7	2166.6	2151.4	2108.9	2046.2	1951.1	1822.5	1700.1	1566.5
27.5°	2072.5	2086.7	2111.0	2123.1	2120.1	2114.0	2078.6	1998.6	1883.3	1737.5	1587.8
30°	1813.4	1865.0	1910.6	1971.3	1989.5	2034.0	2054.3	2008.7	1916.7	1781.1	1615.1
32.5°	1503.8	1578.7	1677.8	1711.2	1768.9	1854.9	1951.1	1968.3	1910.6	1806.4	1632.3
35°	1233.6	1295.3	1372.2	1424.8	1476.5	1616.1	1737.5	1842.8	1862.0	1793.2	1628.2
37.5°	1021.1	1064.6	1132.4	1176.9	1224.5	1343.9	1513.9	1650.5	1746.6	1748.7	1617.1
40°	867.3	886.5	945.2	977.6	1023.1	1126.3	1278.1	1456.2	1596.9	1661.6	1587.8
42.5°	734.7	760.0	808.6	832.8	862.2	952.3	1052.4	1221.4	1395.5	1534.1	1533.1
45°	655.8	674.0	696.2	716.5	749.9	803.5	917.8	1044.3	1211.3	1368.2	1429.9
47.5°	585.9	603.1	625.4	631.5	653.7	704.3	774.2	884.5	1040.3	1196.1	1312.5
50°	527.2	541.4	556.6	567.7	577.8	619.3	671.9	765.0	889.5	1040.3	1185.0
52.5°	481.7	491.8	505.0	511.0	520.1	550.5	591.0	659.8	762.0	899.6	1040.3
55°	439.2	446.3	454.4	464.5	468.5	490.8	522.2	580.9	656.8	780.2	913.8
57.5°	399.7	402.8	407.8	413.9	419.0	438.2	465.5	505.0	571.8	666.9	793.4
60°	355.2	363.3	366.3	372.4	375.4	390.6	411.9	445.3	496.9	578.8	674.0
62.5°	317.8	322.8	327.9	330.9	338.0	343.1	360.3	390.6	433.1	493.8	579.9
65°	284.4	286.4	289.4	292.5	294.5	300.6	316.7	337.0	369.4	423.0	489.8
67.5°	245.9	247.9	252.0	253.0	255.0	263.1	272.2	289.4	316.7	357.2	411.9
70°	208.5	211.5	213.5	215.5	218.6	221.6	231.7	245.9	267.2	295.5	338.0
72.5°	176.1	179.1	179.1	181.1	180.1	184.2	194.3	204.4	218.6	241.9	279.3
75°	143.7	143.7	145.7	146.7	147.7	151.8	155.8	163.9	175.1	193.3	216.6
77.5°	113.3	112.3	114.4	114.4	114.4	117.4	121.4	125.5	132.6	145.7	163.9
80°	83.0	83.0	85.0	86.0	84.0	85.0	87.0	91.1	96.1	105.2	115.4
82.5°	54.6	58.7	57.7	58.7	57.7	59.7	60.7	61.7	63.8	67.8	74.9
85°	33.4	33.4	33.4	34.4	33.4	34.4	34.4	34.4	35.4	37.4	40.5
87.5°	14.2	14.2	14.2	15.2	14.2	14.2	15.2	14.2	15.2	15.2	16.2
90°	15.9	15.4	15.9	15.4	14.8	14.3	13.7	13.2	13.7	12.1	10.4
92.5°	29.7	31.9	33.0	34.9	36.8	42.3	54.4	76.4	102.2	113.2	84.6
95°	69.8	74.8	85.2	95.1	105.0	134.1	197.9	264.4	325.9	290.2	200.1
97.5°	150.1	170.9	207.8	239.1	270.4	343.0	454.6	518.3	501.3	374.3	222.6
100°	365.5	405.7	461.2	500.2	539.2	603.5	648.1	628.8	520.5	351.8	207.2
102.5°	578.8	608.5	648.6	669.8	690.9	721.7	712.4	634.3	484.8	318.8	194.0
105°	719.5	740.4	765.7	772.8	780.0	769.5	714.6	599.7	441.9	293.0	189.1
107.5°	812.4	822.3	825.6	818.2	810.8	767.9	681.6	550.2	404.0	274.3	188.0
110°	858.6	854.2	838.8	819.6	800.3	731.0	629.9	504.0	372.7	264.4	190.7



TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	861.9	845.9	814.6	788.5	762.4	682.7	578.8	463.9	351.8	258.9	196.2
115°	836.6	812.4	771.2	741.2	711.3	630.5	534.8	433.1	338.0	258.3	202.3
117.5°	791.5	764.6	721.7	690.7	659.6	585.4	500.7	412.8	328.7	258.9	210.0
120°	744.8	714.0	670.6	642.8	615.1	549.1	474.9	397.4	322.7	261.1	218.8
122.5°	694.8	667.8	630.5	605.2	579.9	520.0	454.6	384.8	318.8	264.9	227.0
125°	653.0	628.8	593.6	571.7	549.7	496.9	437.0	374.3	315.5	268.8	235.8
127.5°	617.3	596.4	564.5	544.2	523.8	475.5	421.0	364.4	313.9	273.2	243.0
130°	586.5	566.7	537.6	518.9	500.2	455.7	406.2	356.7	312.2	277.6	250.1
132.5°	559.6	539.8	512.8	495.2	477.7	437.0	392.5	349.6	311.7	280.9	256.7
135°	529.9	513.4	486.5	470.8	455.1	419.4	380.4	343.5	311.1	284.2	262.2
137.5°	501.8	484.8	461.7	447.7	433.7	401.8	368.8	338.0	310.0	286.4	266.6
140°	473.3	457.9	437.0	425.2	413.3	387.0	358.9	333.1	309.5	288.6	269.9
142.5°	444.7	431.5	414.4	404.5	394.7	372.7	349.6	328.7	308.4	290.2	273.2
145°	419.4	407.8	394.1	386.2	378.2	360.6	342.4	324.8	307.3	290.8	275.4
147.5°	396.9	388.6	377.6	371.8	366.1	351.2	336.4	321.0	305.6	290.8	277.0
150°	378.7	372.7	364.4	359.2	354.0	342.4	329.8	317.2	303.4	290.8	277.6
152.5°	363.9	358.4	352.3	348.2	344.1	334.2	323.8	312.8	300.7	289.1	278.7
155°	350.7	346.3	341.3	338.0	334.7	326.5	317.7	308.4	297.4	288.0	278.7
157.5°	338.6	335.3	330.9	328.2	325.4	318.8	311.1	303.4	294.6	286.4	279.2
160°	328.1	324.8	321.0	319.1	317.2	311.7	305.6	298.5	291.3	285.3	279.2
162.5°	317.2	314.4	312.2	310.5	308.9	304.0	299.0	293.5	288.0	283.1	278.7
165°	307.8	305.6	303.4	302.0	300.7	296.8	293.5	289.1	284.7	280.9	277.6
167.5°	298.5	296.8	295.7	294.6	293.5	291.3	288.6	284.7	281.4	278.7	277.0
170°	290.2	289.1	288.6	288.0	287.5	285.3	283.6	280.9	278.1	276.5	275.4
172.5°	283.6	282.5	282.5	282.2	282.0	280.3	279.2	277.0	275.4	274.8	274.8
175°	277.6	277.0	277.0	277.0	277.0	275.9	275.4	274.3	273.2	273.2	273.7
177.5°	273.7	273.2	273.7	273.7	273.7	273.2	272.6	272.1	271.5	272.1	273.2
180°	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1072.7	1069.6	1069.6	1067.6	1061.5	1050.4	1049.4	1051.4	1045.4	1039.3	1030.2
5°	1125.3	1106.1	1100.0	1093.9	1081.8	1061.5	1053.5	1046.4	1035.2	1022.1	1007.9
7.5°	1169.8	1142.5	1134.4	1123.3	1099.0	1070.7	1052.4	1037.3	1022.1	1003.9	986.7
10°	1225.5	1186.0	1166.8	1150.6	1117.2	1077.7	1050.4	1028.2	1003.9	981.6	959.3
12.5°	1288.2	1224.5	1218.4	1178.9	1140.5	1081.8	1048.4	1016.0	983.6	956.3	933.0
15°	1340.8	1271.0	1245.7	1219.4	1145.5	1072.7	1040.3	1003.9	966.4	937.1	902.7
17.5°	1374.2	1316.6	1262.9	1227.5	1150.6	1085.8	1023.1	981.6	942.1	901.7	873.3
20°	1414.7	1330.7	1284.2	1236.6	1160.7	1075.7	1013.0	961.4	912.8	876.4	842.0
22.5°	1455.2	1341.9	1303.4	1251.8	1162.7	1065.6	994.8	943.1	887.5	851.1	813.6
25°	1451.2	1358.1	1294.3	1250.8	1142.5	1056.5	973.5	912.8	861.2	814.6	777.2
27.5°	1454.2	1339.8	1275.1	1224.5	1128.3	1043.3	951.2	887.5	833.9	785.3	745.8
30°	1455.2	1312.5	1255.8	1195.1	1102.0	1012.0	925.9	861.2	804.5	751.9	716.5
32.5°	1452.2	1290.3	1219.4	1164.8	1060.5	981.6	896.6	827.8	770.1	721.5	688.1
35°	1445.1	1263.9	1182.0	1113.2	1018.0	938.1	869.3	798.4	736.7	692.2	653.7
37.5°	1425.9	1235.6	1142.5	1074.7	968.4	887.5	826.8	768.1	708.4	655.8	623.4
40°	1411.7	1197.2	1103.0	1029.2	914.8	835.9	785.3	729.6	670.9	623.4	592.0
42.5°	1379.3	1160.7	1062.6	974.5	862.2	781.2	733.7	689.1	638.5	592.0	563.7
45°	1326.7	1121.3	1013.0	923.9	804.5	727.6	684.1	647.7	603.1	558.6	530.3
47.5°	1252.8	1064.6	960.4	871.3	747.8	669.9	626.4	599.1	563.7	526.2	501.9
50°	1172.9	1002.9	906.7	818.7	693.2	617.3	574.8	549.5	526.2	491.8	468.5
52.5°	1068.6	937.1	845.0	761.0	634.5	561.6	524.2	506.0	481.7	457.4	437.2
55°	967.4	852.1	776.2	696.2	576.8	509.0	472.6	453.4	439.2	419.0	402.8
57.5°	850.0	773.1	703.3	630.5	523.2	461.5	427.0	403.8	394.7	385.6	370.4
60°	741.8	683.1	626.4	565.7	467.5	411.9	378.5	360.3	351.2	345.1	335.0
62.5°	642.6	597.1	548.5	499.9	410.9	360.3	335.0	316.7	308.6	307.6	298.5
65°	547.5	515.1	475.6	428.1	358.2	313.7	289.4	278.3	269.2	269.2	262.1
67.5°	452.3	430.1	398.7	365.3	310.7	269.2	246.9	236.8	231.7	231.7	226.7
70°	376.4	361.3	332.9	303.6	256.0	224.7	207.5	198.3	195.3	196.3	192.3
72.5°	305.6	289.4	266.1	244.9	209.5	186.2	174.1	163.9	158.9	159.9	158.9
75°	236.8	228.7	208.5	192.3	163.9	147.7	136.6	131.6	127.5	128.5	126.5
77.5°	178.1	166.0	154.8	143.7	126.5	113.3	104.2	99.2	96.1	96.1	96.1
80°	121.4	119.4	110.3	104.2	90.1	79.9	72.9	71.8	68.8	68.8	68.8
82.5°	78.9	73.9	68.8	64.8	56.7	50.6	47.6	45.5	44.5	43.5	45.5
85°	43.5	40.5	38.5	34.4	31.4	28.3	25.3	24.3	23.3	24.3	23.3
87.5°	17.2	14.2	14.2	13.2	12.1	11.1	11.1	9.1	9.1	8.1	8.1
90°	8.8	7.1	6.6	6.0	4.9	3.3	2.2	1.1	2.2	3.3	4.9
92.5°	55.5	37.9	33.0	28.0	22.5	17.6	12.1	8.2	12.1	17.6	22.5
95°	118.2	71.5	60.8	50.0	35.7	26.4	20.3	18.7	20.3	26.4	35.7
97.5°	127.5	81.3	69.5	57.7	43.4	35.2	30.2	29.7	30.2	35.2	43.4
100°	125.9	87.4	76.7	66.0	52.8	45.1	41.2	40.7	41.2	45.1	52.8
102.5°	128.1	94.5	84.9	75.3	63.8	56.6	53.3	52.2	53.3	56.6	63.8
105°	132.5	102.8	94.2	85.7	75.3	68.7	65.4	63.8	65.4	68.7	75.3
107.5°	139.6	113.2	105.2	97.3	87.4	80.8	77.5	75.9	77.5	80.8	87.4
110°	149.0	124.2	116.5	108.8	99.5	93.4	90.7	89.0	90.7	93.4	99.5

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	158.3	135.8	128.4	120.9	111.6	105.5	102.8	101.1	102.8	105.5	111.6
115°	168.7	147.9	140.4	133.0	123.7	118.2	114.9	112.7	114.9	118.2	123.7
117.5°	179.7	158.9	152.0	145.1	134.7	129.7	127.0	124.2	127.0	129.7	134.7
120°	190.2	170.4	163.6	156.7	146.2	140.7	138.0	136.3	138.0	140.7	146.2
122.5°	201.2	181.9	174.5	167.1	157.2	151.2	148.4	146.8	148.4	151.2	157.2
125°	211.6	192.4	185.0	177.5	167.1	161.1	157.8	156.7	157.8	161.1	167.1
127.5°	221.0	202.3	194.9	187.4	175.9	169.8	166.0	164.3	166.0	169.8	175.9
130°	229.2	211.1	203.6	196.2	184.7	178.1	173.1	171.5	173.1	178.1	184.7
132.5°	236.4	218.8	211.6	204.5	192.9	184.7	179.2	177.0	179.2	184.7	192.9
135°	243.5	226.5	219.0	211.6	200.1	191.8	185.8	183.6	185.8	191.8	200.1
137.5°	248.4	232.0	225.1	218.2	206.7	197.9	191.8	189.6	191.8	197.9	206.7
140°	253.4	237.5	230.6	223.7	212.7	203.9	198.4	195.7	198.4	203.9	212.7
142.5°	257.2	241.9	235.6	229.2	218.2	210.5	204.5	202.3	204.5	210.5	218.2
145°	260.5	246.2	239.9	233.6	224.3	216.0	211.1	209.4	211.1	216.0	224.3
147.5°	263.3	250.1	244.6	239.1	229.8	222.6	217.7	216.6	217.7	222.6	229.8
150°	266.0	253.4	248.4	243.5	235.8	228.7	224.3	223.7	224.3	228.7	235.8
152.5°	267.7	257.2	252.6	247.9	241.3	235.3	230.9	230.9	230.9	235.3	241.3
155°	269.9	260.5	256.6	252.8	246.8	241.3	238.0	238.0	238.0	241.3	246.8
157.5°	271.0	263.3	260.2	257.2	251.7	246.8	244.0	243.5	244.0	246.8	251.7
160°	272.6	266.0	263.2	260.5	256.7	252.3	250.1	250.1	250.1	252.3	256.7
162.5°	273.2	267.7	265.5	263.3	260.0	256.7	255.0	255.0	255.0	256.7	260.0
165°	273.7	269.3	267.4	265.5	263.3	260.5	259.4	260.0	259.4	260.5	263.3
167.5°	273.7	270.4	269.0	267.7	266.0	263.8	263.3	263.8	263.3	263.8	266.0
170°	273.2	270.4	269.8	269.3	268.2	266.6	266.0	267.1	266.0	266.6	268.2
172.5°	273.2	271.0	270.7	270.4	269.9	268.8	268.8	269.3	268.8	268.8	269.9
175°	272.6	271.5	271.2	271.0	271.0	269.9	270.4	271.0	270.4	269.9	271.0
177.5°	272.1	271.5	271.5	271.5	271.5	271.0	271.5	272.1	271.5	271.0	271.5
180°	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1028.2	1027.1	1029.2	1023.1	1013.0	1007.9	993.7	990.7	989.7	990.7	991.7
5°	999.8	998.8	995.8	985.7	973.5	964.4	947.2	946.2	940.1	934.0	937.1
7.5°	972.5	968.4	962.4	949.2	933.0	922.9	908.7	898.6	890.5	885.5	881.4
10°	945.2	939.1	933.0	915.8	895.6	880.4	863.2	855.1	846.0	842.0	837.9
12.5°	909.8	903.7	892.6	872.3	860.2	840.9	823.7	815.6	810.6	802.5	797.4
15°	881.4	869.3	863.2	842.0	816.7	814.6	783.3	781.2	771.1	771.1	763.0
17.5°	849.0	839.9	828.8	807.5	789.3	771.1	754.9	748.9	739.7	737.7	733.7
20°	817.7	805.5	801.5	780.2	761.0	738.7	721.5	715.5	711.4	707.4	710.4
22.5°	785.3	775.2	765.0	745.8	731.6	709.4	699.3	693.2	687.1	685.1	686.1
25°	753.9	744.8	734.7	715.5	700.3	682.1	673.0	669.9	666.9	666.9	665.9
27.5°	723.6	714.4	705.3	688.1	673.0	659.8	652.7	649.7	646.6	648.7	650.7
30°	692.2	684.1	676.0	660.8	648.7	636.5	632.5	630.5	629.4	634.5	634.5
32.5°	663.8	656.8	650.7	636.5	624.4	614.3	611.2	612.2	613.2	616.3	618.3
35°	634.5	629.4	623.4	611.2	601.1	592.0	593.0	593.0	595.0	600.1	604.1
37.5°	608.2	601.1	596.0	585.9	577.8	569.7	572.8	575.8	577.8	583.9	585.9
40°	576.8	573.8	569.7	559.6	552.5	551.5	552.5	554.6	558.6	561.6	564.7
42.5°	551.5	547.5	542.4	534.3	528.2	529.3	530.3	532.3	534.3	539.4	542.4
45°	523.2	520.1	516.1	509.0	504.0	505.0	506.0	506.0	508.0	514.1	516.1
47.5°	491.8	492.8	487.8	480.7	477.6	477.6	477.6	479.7	484.7	486.8	487.8
50°	461.5	459.4	458.4	451.3	449.3	448.3	449.3	450.3	457.4	456.4	459.4
52.5°	429.1	429.1	428.1	424.0	421.0	421.0	419.0	424.0	426.0	428.1	431.1
55°	397.7	394.7	393.7	391.6	387.6	386.6	388.6	394.7	396.7	398.7	401.7
57.5°	363.3	363.3	361.3	358.2	358.2	358.2	358.2	362.3	365.3	367.3	373.4
60°	331.9	327.9	324.8	324.8	324.8	323.8	329.9	329.9	336.0	337.0	339.0
62.5°	294.5	292.5	290.4	291.4	290.4	292.5	294.5	298.5	299.5	302.6	305.6
65°	259.1	259.1	257.0	263.1	259.1	259.1	264.1	264.1	266.1	269.2	273.2
67.5°	224.7	225.7	223.6	223.6	225.7	226.7	227.7	231.7	232.8	236.8	241.9
70°	189.2	191.3	192.3	190.2	192.3	194.3	196.3	197.3	201.4	203.4	206.4
72.5°	157.9	159.9	156.9	157.9	158.9	160.9	161.9	163.9	166.0	172.0	174.1
75°	126.5	125.5	124.5	128.5	126.5	130.5	131.6	131.6	133.6	138.6	140.7
77.5°	97.1	97.1	98.2	96.1	99.2	98.2	99.2	102.2	105.2	105.2	113.3
80°	67.8	69.8	69.8	69.8	70.8	71.8	69.8	74.9	75.9	75.9	78.9
82.5°	43.5	44.5	43.5	45.5	45.5	47.6	46.6	47.6	49.6	51.6	52.6
85°	23.3	23.3	25.3	25.3	24.3	25.3	24.3	25.3	27.3	27.3	28.3
87.5°	8.1	8.1	8.1	8.1	9.1	8.1	9.1	9.1	8.1	8.1	11.1
90°	6.0	6.6	7.1	8.8	10.4	12.1	13.7	13.2	13.7	14.3	14.8
92.5°	28.0	33.0	37.9	55.5	84.6	113.2	102.2	76.4	54.4	42.3	36.8
95°	50.0	60.8	71.5	118.2	200.1	290.2	325.9	264.4	197.9	134.1	105.0
97.5°	57.7	69.5	81.3	127.5	222.6	374.3	501.3	518.3	454.6	343.0	270.4
100°	66.0	76.7	87.4	125.9	207.2	351.8	520.5	628.8	648.1	603.5	539.2
102.5°	75.3	84.9	94.5	128.1	194.0	318.8	484.8	634.3	712.4	721.7	690.9
105°	85.7	94.2	102.8	132.5	189.1	293.0	441.9	599.7	714.6	769.5	780.0
107.5°	97.3	105.2	113.2	139.6	188.0	274.3	404.0	550.2	681.6	767.9	810.8
110°	108.8	116.5	124.2	149.0	190.7	264.4	372.7	504.0	629.9	731.0	800.3

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	120.9	128.4	135.8	158.3	196.2	258.9	351.8	463.9	578.8	682.7	762.4
115°	133.0	140.4	147.9	168.7	202.3	258.3	338.0	433.1	534.8	630.5	711.3
117.5°	145.1	152.0	158.9	179.7	210.0	258.9	328.7	412.8	500.7	585.4	659.6
120°	156.7	163.6	170.4	190.2	218.8	261.1	322.7	397.4	474.9	549.1	615.1
122.5°	167.1	174.5	181.9	201.2	227.0	264.9	318.8	384.8	454.6	520.0	579.9
125°	177.5	185.0	192.4	211.6	235.8	268.8	315.5	374.3	437.0	496.9	549.7
127.5°	187.4	194.9	202.3	221.0	243.0	273.2	313.9	364.4	421.0	475.5	523.8
130°	196.2	203.6	211.1	229.2	250.1	277.6	312.2	356.7	406.2	455.7	500.2
132.5°	204.5	211.6	218.8	236.4	256.7	280.9	311.7	349.6	392.5	437.0	477.7
135°	211.6	219.0	226.5	243.5	262.2	284.2	311.1	343.5	380.4	419.4	455.1
137.5°	218.2	225.1	232.0	248.4	266.6	286.4	310.0	338.0	368.8	401.8	433.7
140°	223.7	230.6	237.5	253.4	269.9	288.6	309.5	333.1	358.9	387.0	413.3
142.5°	229.2	235.6	241.9	257.2	273.2	290.2	308.4	328.7	349.6	372.7	394.7
145°	233.6	239.9	246.2	260.5	275.4	290.8	307.3	324.8	342.4	360.6	378.2
147.5°	239.1	244.6	250.1	263.3	277.0	290.8	305.6	321.0	336.4	351.2	366.1
150°	243.5	248.4	253.4	266.0	277.6	290.8	303.4	317.2	329.8	342.4	354.0
152.5°	247.9	252.6	257.2	267.7	278.7	289.1	300.7	312.8	323.8	334.2	344.1
155°	252.8	256.6	260.5	269.9	278.7	288.0	297.4	308.4	317.7	326.5	334.7
157.5°	257.2	260.2	263.3	271.0	279.2	286.4	294.6	303.4	311.1	318.8	325.4
160°	260.5	263.2	266.0	272.6	279.2	285.3	291.3	298.5	305.6	311.7	317.2
162.5°	263.3	265.5	267.7	273.2	278.7	283.1	288.0	293.5	299.0	304.0	308.9
165°	265.5	267.4	269.3	273.7	277.6	280.9	284.7	289.1	293.5	296.8	300.7
167.5°	267.7	269.0	270.4	273.7	277.0	278.7	281.4	284.7	288.6	291.3	293.5
170°	269.3	269.8	270.4	273.2	275.4	276.5	278.1	280.9	283.6	285.3	287.5
172.5°	270.4	270.7	271.0	273.2	274.8	274.8	275.4	277.0	279.2	280.3	282.0
175°	271.0	271.2	271.5	272.6	273.7	273.2	273.2	274.3	275.4	275.9	277.0
177.5°	271.5	271.5	271.5	272.1	273.2	272.1	271.5	272.1	272.6	273.2	273.7
180°	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	990.7	991.7	987.7	984.6	992.7	987.7	987.7	988.7	986.7	989.7	988.7
5°	935.1	936.1	929.0	931.0	927.0	925.9	924.9	931.0	930.0	929.0	931.0
7.5°	880.4	880.4	877.4	875.3	875.3	872.3	876.4	875.3	877.4	877.4	880.4
10°	834.9	836.9	831.8	826.8	825.8	826.8	826.8	827.8	828.8	835.9	834.9
12.5°	797.4	794.4	793.4	790.3	785.3	783.3	781.2	792.4	789.3	789.3	789.3
15°	755.9	763.0	762.0	752.9	750.9	754.9	752.9	752.9	763.0	762.0	761.0
17.5°	733.7	731.6	729.6	724.6	725.6	724.6	725.6	725.6	731.6	731.6	731.6
20°	708.4	704.3	704.3	702.3	702.3	699.3	703.3	704.3	708.4	708.4	709.4
22.5°	686.1	683.1	683.1	682.1	684.1	680.0	684.1	685.1	685.1	688.1	688.1
25°	666.9	664.9	664.9	666.9	666.9	666.9	666.9	670.9	667.9	668.9	667.9
27.5°	649.7	650.7	651.7	652.7	651.7	652.7	653.7	655.8	656.8	655.8	653.7
30°	633.5	636.5	637.5	637.5	639.6	640.6	641.6	641.6	642.6	639.6	641.6
32.5°	621.3	621.3	623.4	624.4	626.4	627.4	627.4	629.4	628.4	625.4	626.4
35°	604.1	604.1	608.2	610.2	613.2	612.2	613.2	613.2	614.3	612.2	609.2
37.5°	586.9	589.0	589.0	593.0	594.0	595.0	594.0	596.0	595.0	593.0	592.0
40°	566.7	565.7	566.7	569.7	570.7	570.7	570.7	572.8	572.8	572.8	571.8
42.5°	541.4	544.4	543.4	546.5	545.4	545.4	547.5	549.5	550.5	547.5	548.5
45°	517.1	517.1	519.1	519.1	520.1	520.1	524.2	522.2	524.2	522.2	523.2
47.5°	490.8	491.8	491.8	492.8	494.8	496.9	494.8	495.9	495.9	496.9	494.8
50°	461.5	461.5	463.5	466.5	470.6	468.5	467.5	471.6	468.5	468.5	466.5
52.5°	431.1	434.1	435.1	438.2	441.2	442.2	443.2	441.2	442.2	439.2	440.2
55°	401.7	402.8	406.8	409.8	412.9	412.9	411.9	412.9	413.9	409.8	409.8
57.5°	372.4	375.4	379.5	379.5	383.5	383.5	382.5	382.5	383.5	380.5	379.5
60°	341.0	344.1	349.1	349.1	355.2	356.2	354.2	352.2	352.2	349.1	350.1
62.5°	307.6	310.7	313.7	318.8	322.8	320.8	324.8	320.8	321.8	315.7	315.7
65°	278.3	279.3	284.4	289.4	289.4	291.4	289.4	290.4	287.4	287.4	283.3
67.5°	243.9	243.9	248.9	254.0	259.1	259.1	259.1	256.0	256.0	253.0	253.0
70°	213.5	212.5	217.6	220.6	223.6	224.7	222.6	221.6	219.6	216.6	215.5
72.5°	176.1	178.1	183.2	185.2	190.2	189.2	194.3	188.2	188.2	183.2	182.2
75°	142.7	144.7	149.8	152.8	155.8	155.8	158.9	155.8	151.8	149.8	148.8
77.5°	113.3	112.3	116.4	121.4	122.4	121.4	123.5	122.4	118.4	118.4	116.4
80°	81.0	84.0	88.0	87.0	91.1	90.1	90.1	88.0	88.0	85.0	87.0
82.5°	53.6	56.7	57.7	56.7	57.7	59.7	60.7	59.7	59.7	57.7	58.7
85°	28.3	28.3	30.4	31.4	30.4	30.4	31.4	34.4	32.4	30.4	32.4
87.5°	9.1	8.1	8.1	9.1	8.1	8.1	9.1	9.1	10.1	10.1	10.1
90°	15.4	15.9	15.4	15.9	16.5	15.9	16.5	15.9	15.4	15.9	15.4
92.5°	34.9	33.0	31.9	29.7	30.2	29.1	30.2	29.7	31.9	33.0	34.9
95°	95.1	85.2	74.8	69.8	66.0	63.8	66.0	69.8	74.8	85.2	95.1
97.5°	239.1	207.8	170.9	150.1	136.9	130.8	136.9	150.1	170.9	207.8	239.1
100°	500.2	461.2	405.7	365.5	344.1	344.6	344.1	365.5	405.7	461.2	500.2
102.5°	669.8	648.6	608.5	578.8	561.8	545.8	561.8	578.8	608.5	648.6	669.8
105°	772.8	765.7	740.4	719.5	701.9	699.2	701.9	719.5	740.4	765.7	772.8
107.5°	818.2	825.6	822.3	812.4	805.3	799.2	805.3	812.4	822.3	825.6	818.2
110°	819.6	838.8	854.2	858.6	857.5	856.4	857.5	858.6	854.2	838.8	819.6

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	788.5	814.6	845.9	861.9	867.4	867.9	867.4	861.9	845.9	814.6	788.5
115°	741.2	771.2	812.4	836.6	847.6	850.3	847.6	836.6	812.4	771.2	741.2
117.5°	690.7	721.7	764.6	791.5	808.0	811.8	808.0	791.5	764.6	721.7	690.7
120°	642.8	670.6	714.0	744.8	758.0	761.3	758.0	744.8	714.0	670.6	642.8
122.5°	605.2	630.5	667.8	694.8	709.6	714.0	709.6	694.8	667.8	630.5	605.2
125°	571.7	593.6	628.8	653.0	666.7	670.6	666.7	653.0	628.8	593.6	571.7
127.5°	544.2	564.5	596.4	617.3	629.9	633.2	629.9	617.3	596.4	564.5	544.2
130°	518.9	537.6	566.7	586.5	598.0	602.4	598.0	586.5	566.7	537.6	518.9
132.5°	495.2	512.8	539.8	559.6	569.4	572.2	569.4	559.6	539.8	512.8	495.2
135°	470.8	486.5	513.4	529.9	539.8	543.6	539.8	529.9	513.4	486.5	470.8
137.5°	447.7	461.7	484.8	501.8	510.1	513.4	510.1	501.8	484.8	461.7	447.7
140°	425.2	437.0	457.9	473.3	482.1	481.5	482.1	473.3	457.9	437.0	425.2
142.5°	404.5	414.4	431.5	444.7	452.4	451.8	452.4	444.7	431.5	414.4	404.5
145°	386.2	394.1	407.8	419.4	423.8	424.9	423.8	419.4	407.8	394.1	386.2
147.5°	371.8	377.6	388.6	396.9	401.3	401.8	401.3	396.9	388.6	377.6	371.8
150°	359.2	364.4	372.7	378.7	382.0	382.0	382.0	378.7	372.7	364.4	359.2
152.5°	348.2	352.3	358.4	363.9	365.5	365.5	365.5	363.9	358.4	352.3	348.2
155°	338.0	341.3	346.3	350.7	351.8	352.3	351.8	350.7	346.3	341.3	338.0
157.5°	328.2	330.9	335.3	338.6	339.7	339.7	339.7	338.6	335.3	330.9	328.2
160°	319.1	321.0	324.8	328.1	328.1	327.6	328.1	328.1	324.8	321.0	319.1
162.5°	310.5	312.2	314.4	317.2	317.2	316.6	317.2	317.2	314.4	312.2	310.5
165°	302.0	303.4	305.6	307.8	307.3	307.3	307.3	307.8	305.6	303.4	302.0
167.5°	294.6	295.7	296.8	298.5	297.9	297.9	297.9	298.5	296.8	295.7	294.6
170°	288.0	288.6	289.1	290.2	289.7	289.7	289.7	290.2	289.1	288.6	288.0
172.5°	282.2	282.5	282.5	283.6	282.5	282.0	282.5	283.6	282.5	282.5	282.2
175°	277.0	277.0	277.0	277.6	277.0	276.5	277.0	277.6	277.0	277.0	277.0
177.5°	273.7	273.7	273.2	273.7	272.6	272.6	272.6	273.7	273.2	273.7	273.7
180°	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	991.7	993.7	994.8	990.7	987.7	992.7	999.8	1004.9	1008.9	1014.0	1017.0
5°	933.0	940.1	940.1	942.1	945.2	950.2	963.4	972.5	980.6	986.7	991.7
7.5°	883.4	888.5	891.5	896.6	901.7	908.7	923.9	937.1	949.2	956.3	964.4
10°	838.9	843.0	848.0	851.1	860.2	870.3	889.5	900.6	914.8	925.9	936.1
12.5°	796.4	810.6	813.6	812.6	820.7	831.8	851.1	868.3	883.4	894.6	905.7
15°	766.1	771.1	777.2	776.2	793.4	796.4	812.6	832.8	853.1	860.2	870.3
17.5°	732.7	740.8	746.8	749.9	754.9	766.1	781.2	796.4	822.7	823.7	850.0
20°	706.3	714.4	718.5	722.5	725.6	738.7	751.9	769.1	790.3	801.5	815.6
22.5°	689.1	693.2	696.2	699.3	703.3	710.4	726.6	745.8	760.0	772.1	781.2
25°	668.9	673.0	677.0	679.0	682.1	686.1	698.3	713.4	733.7	741.8	750.9
27.5°	654.7	654.7	656.8	656.8	660.8	664.9	674.0	688.1	704.3	714.4	726.6
30°	639.6	638.5	639.6	638.5	637.5	643.6	651.7	663.8	675.0	687.1	695.2
32.5°	624.4	623.4	623.4	624.4	620.3	623.4	627.4	638.5	650.7	656.8	665.9
35°	608.2	606.2	606.2	606.2	604.1	602.1	606.2	616.3	624.4	632.5	639.6
37.5°	592.0	589.0	589.0	586.9	584.9	581.9	581.9	590.0	601.1	604.1	613.2
40°	569.7	569.7	567.7	566.7	564.7	562.7	559.6	566.7	576.8	579.9	586.9
42.5°	547.5	544.4	543.4	543.4	543.4	540.4	538.4	543.4	549.5	554.6	558.6
45°	522.2	520.1	521.2	520.1	518.1	517.1	516.1	518.1	525.2	527.2	532.3
47.5°	494.8	493.8	493.8	492.8	491.8	492.8	488.8	493.8	495.9	497.9	501.9
50°	466.5	465.5	464.5	463.5	463.5	464.5	463.5	463.5	467.5	469.6	473.6
52.5°	438.2	435.1	435.1	434.1	434.1	432.1	434.1	435.1	437.2	439.2	441.2
55°	407.8	407.8	404.8	404.8	402.8	402.8	403.8	402.8	406.8	408.8	408.8
57.5°	378.5	374.4	375.4	373.4	371.4	370.4	370.4	372.4	374.4	374.4	376.4
60°	347.1	343.1	342.0	338.0	340.0	337.0	338.0	338.0	342.0	340.0	342.0
62.5°	315.7	310.7	307.6	305.6	305.6	306.6	304.6	303.6	305.6	307.6	311.7
65°	282.3	279.3	276.3	273.2	273.2	272.2	274.2	271.2	270.2	271.2	273.2
67.5°	247.9	244.9	241.9	238.8	239.8	236.8	234.8	237.8	235.8	236.8	238.8
70°	214.5	212.5	206.4	204.4	203.4	204.4	203.4	201.4	204.4	203.4	204.4
72.5°	181.1	179.1	176.1	171.0	171.0	170.0	169.0	169.0	168.0	168.0	168.0
75°	148.8	144.7	141.7	140.7	138.6	137.6	136.6	134.6	135.6	136.6	134.6
77.5°	115.4	110.3	109.3	109.3	106.3	106.3	107.3	106.3	105.2	105.2	105.2
80°	85.0	81.0	81.0	78.9	76.9	76.9	76.9	76.9	75.9	74.9	75.9
82.5°	54.6	53.6	52.6	52.6	54.6	50.6	52.6	51.6	50.6	50.6	49.6
85°	30.4	31.4	30.4	31.4	29.3	30.4	30.4	30.4	29.3	30.4	28.3
87.5°	11.1	11.1	11.1	12.1	12.1	12.1	12.1	12.1	13.2	12.1	12.1
90°	14.8	14.3	13.7	13.2	13.7	12.1	10.4	8.8	7.1	6.6	6.0
92.5°	36.8	42.3	54.4	76.4	102.2	113.2	84.6	55.5	37.9	33.0	28.0
95°	105.0	134.1	197.9	264.4	325.9	290.2	200.1	118.2	71.5	60.8	50.0
97.5°	270.4	343.0	454.6	518.3	501.3	374.3	222.6	127.5	81.3	69.5	57.7
100°	539.2	603.5	648.1	628.8	520.5	351.8	207.2	125.9	87.4	76.7	66.0
102.5°	690.9	721.7	712.4	634.3	484.8	318.8	194.0	128.1	94.5	84.9	75.3
105°	780.0	769.5	714.6	599.7	441.9	293.0	189.1	132.5	102.8	94.2	85.7
107.5°	810.8	767.9	681.6	550.2	404.0	274.3	188.0	139.6	113.2	105.2	97.3
110°	800.3	731.0	629.9	504.0	372.7	264.4	190.7	149.0	124.2	116.5	108.8

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	762.4	682.7	578.8	463.9	351.8	258.9	196.2	158.3	135.8	128.4	120.9
115°	711.3	630.5	534.8	433.1	338.0	258.3	202.3	168.7	147.9	140.4	133.0
117.5°	659.6	585.4	500.7	412.8	328.7	258.9	210.0	179.7	158.9	152.0	145.1
120°	615.1	549.1	474.9	397.4	322.7	261.1	218.8	190.2	170.4	163.6	156.7
122.5°	579.9	520.0	454.6	384.8	318.8	264.9	227.0	201.2	181.9	174.5	167.1
125°	549.7	496.9	437.0	374.3	315.5	268.8	235.8	211.6	192.4	185.0	177.5
127.5°	523.8	475.5	421.0	364.4	313.9	273.2	243.0	221.0	202.3	194.9	187.4
130°	500.2	455.7	406.2	356.7	312.2	277.6	250.1	229.2	211.1	203.6	196.2
132.5°	477.7	437.0	392.5	349.6	311.7	280.9	256.7	236.4	218.8	211.6	204.5
135°	455.1	419.4	380.4	343.5	311.1	284.2	262.2	243.5	226.5	219.0	211.6
137.5°	433.7	401.8	368.8	338.0	310.0	286.4	266.6	248.4	232.0	225.1	218.2
140°	413.3	387.0	358.9	333.1	309.5	288.6	269.9	253.4	237.5	230.6	223.7
142.5°	394.7	372.7	349.6	328.7	308.4	290.2	273.2	257.2	241.9	235.6	229.2
145°	378.2	360.6	342.4	324.8	307.3	290.8	275.4	260.5	246.2	239.9	233.6
147.5°	366.1	351.2	336.4	321.0	305.6	290.8	277.0	263.3	250.1	244.6	239.1
150°	354.0	342.4	329.8	317.2	303.4	290.8	277.6	266.0	253.4	248.4	243.5
152.5°	344.1	334.2	323.8	312.8	300.7	289.1	278.7	267.7	257.2	252.6	247.9
155°	334.7	326.5	317.7	308.4	297.4	288.0	278.7	269.9	260.5	256.6	252.8
157.5°	325.4	318.8	311.1	303.4	294.6	286.4	279.2	271.0	263.3	260.2	257.2
160°	317.2	311.7	305.6	298.5	291.3	285.3	279.2	272.6	266.0	263.2	260.5
162.5°	308.9	304.0	299.0	293.5	288.0	283.1	278.7	273.2	267.7	265.5	263.3
165°	300.7	296.8	293.5	289.1	284.7	280.9	277.6	273.7	269.3	267.4	265.5
167.5°	293.5	291.3	288.6	284.7	281.4	278.7	277.0	273.7	270.4	269.0	267.7
170°	287.5	285.3	283.6	280.9	278.1	276.5	275.4	273.2	270.4	269.8	269.3
172.5°	282.0	280.3	279.2	277.0	275.4	274.8	274.8	273.2	271.0	270.7	270.4
175°	277.0	275.9	275.4	274.3	273.2	273.2	273.7	272.6	271.5	271.2	271.0
177.5°	273.7	273.2	272.6	272.1	271.5	272.1	273.2	272.1	271.5	271.5	271.5
180°	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5	271.5

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1044.3	1044.3	1044.3	1044.3
2.5°	1022.1	1025.1	1035.2	1047.4
5°	1001.8	1009.9	1024.1	1043.3
7.5°	979.6	991.7	1012.0	1036.2
10°	954.3	971.5	996.8	1027.1
12.5°	927.0	949.2	981.6	1013.0
15°	909.8	932.0	961.4	995.8
17.5°	876.4	902.7	933.0	981.6
20°	842.0	871.3	910.8	959.3
22.5°	815.6	847.0	884.5	936.1
25°	784.3	816.7	857.1	910.8
27.5°	750.9	783.3	828.8	885.5
30°	725.6	756.9	800.5	861.2
32.5°	695.2	725.6	771.1	834.9
35°	660.8	695.2	738.7	803.5
37.5°	634.5	665.9	711.4	773.1
40°	606.2	633.5	678.0	738.7
42.5°	575.8	606.2	644.6	705.3
45°	547.5	569.7	609.2	666.9
47.5°	517.1	542.4	572.8	617.3
50°	484.7	506.0	539.4	569.7
52.5°	453.4	470.6	498.9	522.2
55°	420.0	437.2	458.4	472.6
57.5°	388.6	400.7	414.9	424.0
60°	350.1	362.3	371.4	380.5
62.5°	315.7	324.8	329.9	335.0
65°	280.3	285.4	288.4	292.5
67.5°	241.9	246.9	247.9	254.0
70°	206.4	207.5	209.5	212.5
72.5°	173.0	175.1	174.1	176.1
75°	138.6	140.7	138.6	140.7
77.5°	105.2	107.3	107.3	110.3
80°	75.9	76.9	77.9	77.9
82.5°	49.6	52.6	50.6	51.6
85°	28.3	29.3	29.3	30.4
87.5°	13.2	14.2	13.2	15.2
90°	4.9	3.3	2.2	1.1
92.5°	22.5	17.6	12.1	8.2
95°	35.7	26.4	20.3	18.7
97.5°	43.4	35.2	30.2	29.7
100°	52.8	45.1	41.2	40.7
102.5°	63.8	56.6	53.3	52.2
105°	75.3	68.7	65.4	63.8
107.5°	87.4	80.8	77.5	75.9
110°	99.5	93.4	90.7	89.0

TEST NUMBER: P1012065

CATALOG NUMBER: S123DIP-B775D585UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	111.6	105.5	102.8	101.1
115°	123.7	118.2	114.9	112.7
117.5°	134.7	129.7	127.0	124.2
120°	146.2	140.7	138.0	136.3
122.5°	157.2	151.2	148.4	146.8
125°	167.1	161.1	157.8	156.7
127.5°	175.9	169.8	166.0	164.3
130°	184.7	178.1	173.1	171.5
132.5°	192.9	184.7	179.2	177.0
135°	200.1	191.8	185.8	183.6
137.5°	206.7	197.9	191.8	189.6
140°	212.7	203.9	198.4	195.7
142.5°	218.2	210.5	204.5	202.3
145°	224.3	216.0	211.1	209.4
147.5°	229.8	222.6	217.7	216.6
150°	235.8	228.7	224.3	223.7
152.5°	241.3	235.3	230.9	230.9
155°	246.8	241.3	238.0	238.0
157.5°	251.7	246.8	244.0	243.5
160°	256.7	252.3	250.1	250.1
162.5°	260.0	256.7	255.0	255.0
165°	263.3	260.5	259.4	260.0
167.5°	266.0	263.8	263.3	263.8
170°	268.2	266.6	266.0	267.1
172.5°	269.9	268.8	268.8	269.3
175°	271.0	269.9	270.4	271.0
177.5°	271.5	271.0	271.5	272.1
180°	271.5	271.5	271.5	271.5

(END OF REPORT)