

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012146

Luminaire Tested: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012146
REPORT IS A COMBINATION OF REPORTS P992761 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8182.0 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	94	90	87	90	86	83	80	73	71	69	60	59	57	49	48	47
2	90	82	77	72	82	76	71	67	64	61	58	54	51	49	43	42	40
3	82	73	66	60	75	68	61	57	57	53	49	48	45	42	39	37	35
4	75	65	57	52	69	60	54	48	51	46	42	43	39	36	35	33	30
5	69	58	50	45	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	29	26	24
7	59	47	40	34	54	44	37	32	38	33	29	32	28	25	27	24	21
8	55	43	36	30	51	40	33	29	35	29	26	30	25	22	25	22	19
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16863	16863	16863	16863
5°	16876	19422	16919	14409
10°	16727	23445	16800	12585
15°	16554	26609	16554	11097
20°	16216	28701	16306	9844
25°	15967	27268	15936	8982
30°	15678	18893	15645	8139
35°	15329	12130	15261	7504
40°	14897	8566	14824	6872
45°	14143	6854	14123	6256
50°	13217	5735	13173	5536
55°	12176	4726	12078	4694
60°	11153	3907	11043	3992
65°	9955	3126	10020	3384
70°	8846	2173	9085	2735
75°	7501	1612	7806	2104
80°	5972	1068	6482	1578
85°	4255	505	4639	982

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 22513 cd/sqm

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.9	1.9
10°-20°	481.6	5.9
20°-30°	758.5	9.3
30°-40°	788.7	9.6
40°-50°	674.8	8.2
50°-60°	514.5	6.3
60°-70°	329.6	4.0
70°-80°	157.9	1.9
80°-90°	44.7	0.5
90°-100°	308.6	3.8
100°-110°	903.5	11.0
110°-120°	882.3	10.8
120°-130°	702.7	8.6
130°-140°	554.4	6.8
140°-150°	413.6	5.1
150°-160°	288.4	3.5
160°-170°	169.4	2.1
170°-180°	55.1	0.7
0°-30°	1394.0	17.0
0°-40°	2182.7	26.7
0°-60°	3372.0	41.2
0°-90°	3904.1	47.7
90°-120°	2094.4	25.6
90°-150°	3765.0	46.0
90°-180°	4278.0	52.3
0°-180°	8182.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1567	1567	1567	1567	1567	
5°	1565	1860	1569	1380	1565	148
15°	1496	2644	1496	1102	1496	421
25°	1360	2724	1357	897	1360	626
35°	1187	1182	1182	731	1187	743
45°	952	630	951	575	952	733
55°	672	396	667	393	672	602
65°	412	228	414	247	412	411
75°	197	97	205	126	197	213
85°	44	23	48	44	44	49
90°	2	33	2	33	2	5
95°	39	134	39	134	39	41
105°	134	1464	134	1464	134	142
115°	236	1781	236	1781	236	234
125°	328	1404	328	1404	328	291
135°	384	1139	384	1139	384	297
145°	439	890	439	890	439	275
155°	498	738	498	738	498	229
165°	544	644	544	644	544	153
175°	568	579	568	579	568	54
180°	569	569	569	569	569	

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6
2.5°	1570.7	1581.4	1589.4	1594.8	1608.2	1616.3	1623.0	1635.0	1635.0	1637.7	1643.1
5°	1565.3	1588.1	1604.2	1625.6	1653.8	1667.2	1686.0	1702.1	1724.9	1737.0	1749.0
7.5°	1553.2	1585.4	1618.9	1651.1	1692.7	1719.5	1738.3	1779.9	1809.4	1845.6	1873.8
10°	1537.1	1581.4	1624.3	1673.9	1730.3	1770.5	1798.7	1853.7	1910.0	1961.0	2003.9
12.5°	1517.0	1570.7	1632.4	1692.7	1771.8	1812.1	1857.7	1926.1	2006.6	2071.0	2128.6
15°	1495.5	1557.2	1627.0	1700.8	1800.0	1856.4	1922.1	2005.2	2095.1	2187.7	2266.8
17.5°	1462.0	1539.8	1617.6	1724.9	1841.6	1875.1	1931.5	2045.5	2156.8	2240.0	2336.5
20°	1428.5	1515.7	1613.6	1710.2	1836.2	1914.0	1966.3	2087.1	2206.4	2307.0	2399.6
22.5°	1397.6	1488.8	1590.8	1712.8	1830.9	1908.7	1974.4	2100.5	2238.6	2351.3	2465.3
25°	1360.1	1459.3	1572.0	1687.3	1830.9	1889.9	1962.3	2108.5	2254.7	2384.8	2525.7
27.5°	1319.8	1420.4	1531.8	1649.8	1781.2	1868.4	1939.5	2096.4	2274.8	2414.3	2559.2
30°	1279.6	1382.9	1490.2	1596.1	1743.7	1826.8	1908.7	2081.7	2285.6	2445.2	2556.5
32.5°	1240.7	1327.9	1433.8	1537.1	1683.3	1774.5	1867.1	2066.9	2289.6	2423.7	2477.4
35°	1187.0	1278.3	1364.1	1474.1	1621.6	1711.5	1820.1	2065.6	2272.2	2355.3	2328.5
37.5°	1137.4	1213.9	1295.7	1393.6	1545.2	1661.9	1774.5	2030.7	2214.5	2219.8	2068.3
40°	1082.4	1145.5	1213.9	1317.2	1480.8	1596.1	1718.2	1977.1	2109.9	2030.7	1763.8
42.5°	1019.4	1075.7	1129.4	1230.0	1408.4	1537.1	1668.6	1910.0	1958.3	1775.9	1498.2
45°	952.3	997.9	1047.6	1153.5	1331.9	1459.3	1590.8	1806.7	1757.1	1499.6	1235.3
47.5°	882.6	921.5	969.8	1066.3	1250.1	1380.2	1504.9	1659.2	1533.1	1256.8	1035.5
50°	812.8	843.7	890.6	989.9	1166.9	1285.0	1400.3	1500.9	1323.9	1078.4	855.7
52.5°	744.4	768.6	816.8	901.3	1073.0	1185.7	1268.9	1307.8	1128.0	890.6	743.1
55°	672.0	698.8	731.0	816.8	987.2	1070.4	1125.3	1124.0	938.9	755.1	614.3
57.5°	602.2	626.4	654.6	740.4	878.5	934.9	981.8	959.0	783.3	618.3	527.1
60°	540.5	554.0	584.8	657.2	761.9	810.1	837.0	798.1	639.8	521.8	435.9
62.5°	473.5	486.9	512.4	580.8	645.2	670.6	693.4	643.8	528.5	425.2	372.9
65°	411.8	429.2	445.3	500.3	535.2	566.0	563.3	521.8	413.1	346.1	303.1
67.5°	358.1	364.8	378.2	411.8	427.9	450.7	452.0	405.1	332.6	281.7	256.2
70°	300.4	307.2	316.5	332.6	343.4	348.7	346.1	304.5	250.8	220.0	197.2
72.5°	250.8	249.5	256.2	256.2	266.9	265.6	257.5	225.3	190.5	165.0	151.6
75°	197.2	198.5	199.9	197.2	193.1	187.8	181.1	156.9	134.1	122.1	110.0
77.5°	154.2	151.6	152.9	143.5	138.2	132.8	123.4	111.3	92.5	89.9	84.5
80°	110.0	108.6	107.3	103.3	91.2	85.8	79.1	72.4	68.4	65.7	64.4
82.5°	73.8	73.8	71.1	63.0	56.3	52.3	51.0	48.3	44.3	44.3	42.9
85°	44.3	42.9	40.2	32.2	28.2	28.2	28.2	28.2	25.5	25.5	24.1
87.5°	17.4	16.1	12.1	12.1	10.7	10.7	10.7	9.4	9.4	8.0	8.0
90°	2.3	4.6	6.9	10.4	12.7	13.8	15.0	18.4	21.9	25.3	28.8
92.5°	17.3	25.3	36.8	47.2	58.7	69.1	79.4	116.3	177.3	237.2	214.1
95°	39.1	42.6	55.3	74.8	104.8	127.2	149.7	247.5	419.0	607.8	682.7
97.5°	62.2	63.3	73.7	90.9	120.9	145.6	170.4	267.1	466.2	784.0	1049.9
100°	85.2	86.3	94.4	110.5	138.1	160.6	183.0	263.6	434.0	736.8	1090.2
102.5°	109.4	111.7	118.6	133.5	157.7	177.8	198.0	268.2	406.4	667.7	1015.4
105°	133.5	137.0	143.9	157.7	179.6	197.4	215.3	277.4	396.0	613.6	925.6
107.5°	158.9	162.3	169.2	183.0	203.8	220.5	237.2	292.4	393.7	574.5	846.1
110°	186.5	190.0	195.7	208.4	227.9	244.0	260.2	312.0	399.5	553.7	780.5

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	211.8	215.3	221.0	233.7	253.3	268.8	284.4	331.6	411.0	542.2	736.8
115°	236.0	240.6	247.5	259.0	278.6	294.2	309.7	353.4	423.7	541.1	708.0
117.5°	260.2	265.9	271.7	282.0	303.9	318.3	332.7	376.4	439.8	542.2	688.4
120°	285.5	289.0	294.7	306.2	328.1	342.5	356.9	398.3	458.2	546.8	675.8
122.5°	307.4	310.8	316.6	329.2	350.0	365.6	381.1	421.3	475.5	554.9	667.7
125°	328.1	330.4	337.3	350.0	371.8	387.4	402.9	443.2	493.9	562.9	660.8
127.5°	344.2	347.7	355.7	368.4	392.6	408.2	423.7	462.8	508.8	572.2	657.3
130°	359.2	362.6	373.0	386.8	411.0	426.6	442.1	480.1	523.8	581.4	653.9
132.5°	370.7	375.3	386.8	404.1	428.3	443.2	458.2	495.0	537.6	588.3	652.7
135°	384.5	389.1	401.8	419.0	443.2	458.8	474.3	510.0	549.1	595.2	651.6
137.5°	397.2	401.8	414.4	432.9	457.0	471.4	485.8	520.4	558.3	599.8	649.3
140°	409.8	415.6	427.1	445.5	468.5	482.9	497.3	530.7	565.3	604.4	648.1
142.5°	423.7	428.3	440.9	457.0	480.1	493.3	506.5	538.8	572.2	607.8	645.8
145°	438.6	442.1	452.4	469.7	489.3	502.5	515.7	545.7	576.8	609.0	643.5
147.5°	453.6	455.9	466.2	481.2	500.8	512.3	523.8	551.4	580.2	609.0	640.1
150°	468.5	469.7	478.9	493.9	510.0	520.4	530.7	557.2	581.4	609.0	635.5
152.5°	483.5	483.5	492.7	505.4	519.2	529.0	538.8	560.6	583.7	605.5	629.7
155°	498.5	498.5	505.4	516.9	529.6	537.7	545.7	565.3	583.7	603.2	622.8
157.5°	510.0	511.1	516.9	527.3	538.8	545.1	551.4	567.6	584.8	599.8	617.1
160°	523.8	523.8	528.4	537.6	545.7	551.4	557.2	571.0	584.8	597.5	610.1
162.5°	534.2	534.2	537.6	544.5	551.4	556.0	560.6	572.2	583.7	592.9	603.2
165°	544.5	543.4	545.7	551.4	556.0	560.0	564.1	573.3	581.4	588.3	596.3
167.5°	552.6	551.4	552.6	557.2	560.6	563.5	566.4	573.3	580.2	583.7	589.4
170°	559.5	557.2	558.3	561.8	564.1	565.2	566.4	572.2	576.8	579.1	582.5
172.5°	564.1	562.9	562.9	565.3	566.4	567.0	567.6	572.2	575.6	575.6	576.8
175°	567.6	566.4	565.3	567.6	567.6	568.2	568.7	571.0	573.3	572.2	572.2
177.5°	569.9	568.7	567.6	568.7	568.7	568.7	568.7	569.9	572.2	569.9	568.7
180°	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6
2.5°	1653.8	1653.8	1665.9	1678.0	1671.3	1675.3	1690.0	1684.7	1695.4	1694.1	1698.1
5°	1778.6	1793.3	1805.4	1830.9	1834.9	1830.9	1856.4	1863.1	1875.1	1860.4	1867.1
7.5°	1919.4	1950.2	1979.8	2017.3	2029.4	2032.1	2045.5	2064.3	2080.3	2050.8	2065.6
10°	2056.2	2103.1	2163.5	2197.0	2226.5	2237.3	2248.0	2260.1	2278.9	2296.3	2282.9
12.5°	2203.7	2272.2	2329.8	2390.2	2426.4	2422.4	2453.2	2461.3	2476.0	2480.1	2485.4
15°	2324.5	2421.0	2457.3	2547.1	2555.2	2582.0	2616.9	2647.7	2651.7	2643.7	2643.7
17.5°	2439.8	2523.0	2587.4	2659.8	2674.5	2697.3	2741.6	2756.4	2761.7	2760.4	2760.4
20°	2533.7	2588.7	2697.3	2757.7	2781.8	2811.4	2842.2	2861.0	2865.0	2870.4	2862.3
22.5°	2595.4	2678.6	2767.1	2816.7	2836.8	2847.6	2867.7	2873.1	2866.3	2867.7	2869.0
25°	2643.7	2725.5	2779.2	2792.6	2791.2	2777.8	2763.1	2737.6	2734.9	2724.2	2702.7
27.5°	2657.1	2688.0	2681.2	2626.3	2571.3	2565.9	2477.4	2429.1	2374.1	2382.1	2351.3
30°	2584.7	2544.4	2449.2	2309.7	2252.0	2158.1	2058.9	1955.6	1915.4	1871.1	1952.9
32.5°	2407.6	2264.1	2095.1	1914.0	1817.5	1734.3	1628.3	1553.2	1510.3	1474.1	1543.8
35°	2140.7	1916.7	1692.7	1521.0	1441.9	1366.8	1267.5	1230.0	1176.3	1181.7	1188.4
37.5°	1797.3	1550.5	1381.5	1212.5	1160.2	1129.4	1056.9	999.3	980.5	975.1	975.1
40°	1475.4	1272.9	1122.7	989.9	949.6	924.2	866.5	839.7	819.5	814.2	820.9
42.5°	1220.6	1047.6	930.9	842.3	814.2	782.0	757.8	724.3	720.3	710.9	723.0
45°	1024.7	874.5	787.3	723.0	698.8	686.7	659.9	639.8	631.7	630.4	639.8
47.5°	869.2	752.5	676.0	635.8	617.0	604.9	582.1	574.1	566.0	568.7	564.7
50°	729.7	642.5	592.9	556.6	544.6	532.5	517.7	509.7	505.7	505.7	504.3
52.5°	626.4	554.0	521.8	488.2	482.9	476.2	460.1	454.7	448.0	446.7	452.0
55°	536.5	486.9	454.7	434.6	429.2	415.8	409.1	402.4	398.4	395.7	397.0
57.5°	458.7	421.2	399.7	382.3	372.9	367.5	355.4	354.1	351.4	351.4	350.1
60°	394.3	367.5	342.0	331.3	324.6	317.9	316.5	308.5	304.5	307.2	305.8
62.5°	334.0	312.5	297.8	285.7	281.7	276.3	272.3	269.6	265.6	266.9	266.9
65°	279.0	261.6	250.8	240.1	238.8	233.4	232.0	229.4	229.4	228.0	230.7
67.5°	229.4	217.3	207.9	201.2	197.2	198.5	193.1	189.1	189.1	187.8	191.8
70°	182.4	175.7	166.3	158.3	152.9	152.9	146.2	144.9	144.9	144.9	143.5
72.5°	140.8	128.8	124.7	122.1	122.1	122.1	119.4	119.4	118.0	119.4	118.0
75°	104.6	103.3	100.6	99.3	99.3	97.9	96.6	96.6	96.6	96.6	96.6
77.5°	81.8	81.8	79.1	77.8	77.8	77.8	76.5	76.5	75.1	75.1	75.1
80°	60.4	60.4	57.7	57.7	57.7	56.3	56.3	56.3	57.7	56.3	56.3
82.5°	41.6	41.6	40.2	41.6	40.2	38.9	38.9	38.9	37.6	38.9	38.9
85°	24.1	24.1	22.8	21.5	22.8	22.8	21.5	22.8	21.5	22.8	21.5
87.5°	9.4	8.0	8.0	8.0	6.7	8.0	6.7	6.7	8.0	6.7	8.0
90°	27.6	28.8	29.9	31.1	32.2	33.4	32.2	33.4	34.5	33.4	34.5
92.5°	160.0	114.0	88.6	77.1	73.1	69.1	66.8	62.2	63.3	61.0	63.3
95°	553.7	414.4	280.9	219.9	199.2	178.4	156.6	146.2	138.1	133.5	138.1
97.5°	1085.6	952.1	718.4	566.4	500.8	435.2	358.0	314.3	286.7	274.0	286.7
100°	1317.0	1357.3	1264.0	1129.3	1047.6	965.9	849.6	765.6	720.7	721.8	720.7
102.5°	1328.5	1492.0	1511.6	1447.1	1402.8	1358.4	1274.4	1212.2	1176.6	1143.2	1176.6
105°	1256.0	1496.6	1611.7	1633.6	1618.6	1603.7	1550.7	1507.0	1470.1	1464.4	1470.1
107.5°	1152.4	1427.5	1608.3	1698.1	1713.6	1729.1	1722.2	1701.5	1686.5	1673.9	1686.5
110°	1055.7	1319.3	1531.1	1676.2	1716.5	1756.8	1789.0	1798.2	1795.9	1793.6	1795.9

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	971.6	1212.2	1429.8	1596.7	1651.4	1706.1	1771.7	1805.1	1816.6	1817.8	1816.6
115°	907.2	1120.1	1320.5	1489.7	1552.4	1615.2	1701.5	1752.2	1775.2	1780.9	1775.2
117.5°	864.6	1048.8	1226.1	1381.5	1446.6	1511.6	1601.4	1657.8	1692.3	1700.4	1692.3
120°	832.3	994.7	1150.1	1288.2	1346.4	1404.5	1495.4	1559.9	1587.5	1594.4	1587.5
122.5°	805.9	952.1	1089.1	1214.5	1267.5	1320.5	1398.7	1455.1	1486.2	1495.4	1486.2
125°	784.0	915.2	1040.7	1151.2	1197.2	1243.3	1317.0	1367.7	1396.4	1404.5	1396.4
127.5°	763.3	881.8	995.8	1097.1	1139.7	1182.3	1249.1	1292.8	1319.3	1326.2	1319.3
130°	747.1	850.8	954.4	1047.6	1086.8	1125.9	1186.9	1228.4	1252.5	1261.7	1252.5
132.5°	732.2	822.0	915.2	1000.4	1037.2	1074.1	1130.5	1171.9	1192.7	1198.4	1192.7
135°	719.5	796.6	878.4	953.2	986.0	1018.8	1075.2	1109.8	1130.5	1138.6	1130.5
137.5°	708.0	772.5	841.5	908.3	937.6	967.0	1015.4	1051.1	1068.3	1075.2	1068.3
140°	697.6	751.7	810.5	865.7	890.4	915.2	959.0	991.2	1009.6	1008.5	1009.6
142.5°	688.4	732.2	780.5	826.6	847.3	868.0	903.7	931.3	947.5	946.3	947.5
145°	680.4	717.2	755.2	792.0	808.7	825.4	854.2	878.4	887.6	889.9	887.6
147.5°	672.3	704.5	735.6	766.7	778.8	790.9	813.9	831.2	840.4	841.5	840.4
150°	664.3	690.7	717.2	741.4	752.3	763.3	780.5	793.2	800.1	800.1	800.1
152.5°	655.0	678.1	699.9	720.7	729.3	737.9	750.6	762.1	765.6	765.6	765.6
155°	645.8	665.4	683.8	701.1	708.0	714.9	725.3	734.5	736.8	737.9	736.8
157.5°	635.5	651.6	667.7	681.5	687.2	693.0	702.2	709.2	711.5	711.5	711.5
160°	625.1	640.1	652.7	664.3	668.3	672.3	680.4	687.3	687.3	686.1	687.3
162.5°	614.8	626.3	636.6	647.0	650.4	653.9	658.5	664.3	664.3	663.1	664.3
165°	605.5	614.8	621.7	629.7	632.6	635.5	640.1	644.7	643.5	643.5	643.5
167.5°	596.3	604.4	610.1	614.8	617.1	619.4	621.7	625.1	624.0	624.0	624.0
170°	588.3	594.0	597.5	602.1	603.2	604.4	605.5	607.8	606.7	606.7	606.7
172.5°	580.2	584.8	587.1	590.6	591.2	591.7	591.7	594.0	591.7	590.6	591.7
175°	574.5	576.8	577.9	580.2	580.2	580.2	580.2	581.4	580.2	579.1	580.2
177.5°	569.9	571.0	572.2	573.3	573.3	573.3	572.2	573.3	571.0	571.0	571.0
180°	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6
2.5°	1691.4	1683.3	1678.0	1673.9	1669.9	1682.0	1665.9	1648.5	1636.4	1628.3	1625.6
5°	1868.4	1851.0	1836.2	1824.2	1826.8	1826.8	1798.7	1767.8	1741.0	1726.2	1710.2
7.5°	2073.6	2054.9	2025.4	2018.6	2013.3	1979.8	1951.6	1895.2	1861.7	1828.2	1798.7
10°	2277.5	2253.4	2225.2	2215.8	2202.4	2160.8	2117.9	2045.5	2003.9	1942.2	1903.3
12.5°	2468.0	2438.5	2410.3	2403.6	2383.5	2347.3	2273.5	2198.4	2127.3	2061.6	1993.2
15°	2627.6	2619.5	2576.6	2549.8	2505.5	2455.9	2439.8	2337.9	2248.0	2179.6	2056.2
17.5°	2761.7	2724.2	2683.9	2666.5	2649.1	2591.4	2533.7	2429.1	2332.5	2231.9	2152.8
20°	2869.0	2827.4	2799.3	2773.8	2765.7	2700.0	2608.8	2516.3	2410.3	2297.6	2194.4
22.5°	2874.4	2869.0	2850.3	2835.5	2819.4	2776.5	2704.0	2588.7	2476.0	2352.6	2217.2
25°	2763.1	2755.0	2808.7	2795.3	2806.0	2789.9	2751.0	2654.4	2523.0	2378.1	2241.3
27.5°	2427.7	2509.6	2594.1	2623.6	2643.7	2701.4	2720.1	2666.5	2560.5	2406.3	2253.4
30°	1971.7	2080.3	2217.2	2290.9	2347.3	2454.6	2594.1	2611.5	2561.9	2438.5	2250.7
32.5°	1547.9	1647.1	1757.1	1844.3	1919.4	2139.4	2327.1	2462.6	2486.8	2422.4	2257.4
35°	1247.4	1290.3	1394.9	1478.1	1580.0	1767.8	1989.1	2207.8	2355.3	2363.4	2237.3
37.5°	1028.8	1051.6	1142.8	1189.7	1250.1	1415.1	1621.6	1907.3	2136.7	2245.3	2180.9
40°	851.7	904.0	956.3	983.2	1026.1	1140.1	1338.6	1562.6	1847.0	2048.2	2093.8
42.5°	739.1	761.9	795.4	832.9	859.8	959.0	1091.8	1297.0	1553.2	1833.5	1959.6
45°	651.9	659.9	694.8	718.9	747.1	816.8	910.7	1082.4	1307.8	1584.1	1798.7
47.5°	579.4	595.5	614.3	629.1	647.8	701.5	782.0	906.7	1105.2	1352.0	1582.7
50°	515.1	524.4	548.6	555.3	568.7	606.3	668.0	763.2	926.8	1124.0	1362.8
52.5°	454.7	472.1	481.5	490.9	503.0	533.8	574.1	651.9	775.3	960.4	1162.9
55°	407.8	413.1	426.5	434.6	444.0	465.4	500.3	558.0	654.6	802.1	993.9
57.5°	362.1	362.1	375.6	382.3	391.7	407.8	438.6	482.9	552.6	662.6	838.3
60°	313.9	315.2	325.9	334.0	336.7	352.8	378.2	413.1	466.8	547.2	690.8
62.5°	270.9	277.6	283.0	285.7	295.1	304.5	325.9	350.1	387.6	458.7	560.7
65°	234.7	236.1	240.1	242.8	246.8	257.5	273.6	289.7	321.9	374.2	457.4
67.5°	193.1	198.5	203.9	203.9	207.9	213.3	229.4	242.8	266.9	297.8	354.1
70°	144.9	147.5	155.6	159.6	165.0	174.4	182.4	190.5	209.2	232.0	275.0
72.5°	120.7	120.7	123.4	124.7	124.7	131.4	143.5	151.6	161.0	177.1	206.6
75°	96.6	96.6	100.6	99.3	101.9	104.6	106.0	111.3	116.7	128.8	146.2
77.5°	76.5	77.8	77.8	79.1	79.1	80.5	81.8	84.5	87.2	93.9	101.9
80°	56.3	57.7	57.7	59.0	59.0	60.4	61.7	63.0	65.7	68.4	72.4
82.5°	38.9	40.2	40.2	41.6	40.2	41.6	42.9	42.9	44.3	46.9	48.3
85°	22.8	22.8	24.1	22.8	22.8	22.8	24.1	24.1	25.5	29.5	29.5
87.5°	6.7	8.0	6.7	8.0	8.0	8.0	8.0	9.4	9.4	10.7	12.1
90°	33.4	32.2	33.4	32.2	31.1	29.9	28.8	27.6	28.8	25.3	21.9
92.5°	62.2	66.8	69.1	73.1	77.1	88.6	114.0	160.0	214.1	237.2	177.3
95°	146.2	156.6	178.4	199.2	219.9	280.9	414.4	553.7	682.7	607.8	419.0
97.5°	314.3	358.0	435.2	500.8	566.4	718.4	952.1	1085.6	1049.9	784.0	466.2
100°	765.6	849.6	965.9	1047.6	1129.3	1264.0	1357.3	1317.0	1090.2	736.8	434.0
102.5°	1212.2	1274.4	1358.4	1402.8	1447.1	1511.6	1492.0	1328.5	1015.4	667.7	406.4
105°	1507.0	1550.7	1603.7	1618.6	1633.6	1611.7	1496.6	1256.0	925.6	613.6	396.0
107.5°	1701.5	1722.2	1729.1	1713.6	1698.1	1608.3	1427.5	1152.4	846.1	574.5	393.7
110°	1798.2	1789.0	1756.8	1716.5	1676.2	1531.1	1319.3	1055.7	780.5	553.7	399.5

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1805.1	1771.7	1706.1	1651.4	1596.7	1429.8	1212.2	971.6	736.8	542.2	411.0
115°	1752.2	1701.5	1615.2	1552.4	1489.7	1320.5	1120.1	907.2	708.0	541.1	423.7
117.5°	1657.8	1601.4	1511.6	1446.6	1381.5	1226.1	1048.8	864.6	688.4	542.2	439.8
120°	1559.9	1495.4	1404.5	1346.4	1288.2	1150.1	994.7	832.3	675.8	546.8	458.2
122.5°	1455.1	1398.7	1320.5	1267.5	1214.5	1089.1	952.1	805.9	667.7	554.9	475.5
125°	1367.7	1317.0	1243.3	1197.2	1151.2	1040.7	915.2	784.0	660.8	562.9	493.9
127.5°	1292.8	1249.1	1182.3	1139.7	1097.1	995.8	881.8	763.3	657.3	572.2	508.8
130°	1228.4	1186.9	1125.9	1086.8	1047.6	954.4	850.8	747.1	653.9	581.4	523.8
132.5°	1171.9	1130.5	1074.1	1037.2	1000.4	915.2	822.0	732.2	652.7	588.3	537.6
135°	1109.8	1075.2	1018.8	986.0	953.2	878.4	796.6	719.5	651.6	595.2	549.1
137.5°	1051.1	1015.4	967.0	937.6	908.3	841.5	772.5	708.0	649.3	599.8	558.3
140°	991.2	959.0	915.2	890.4	865.7	810.5	751.7	697.6	648.1	604.4	565.3
142.5°	931.3	903.7	868.0	847.3	826.6	780.5	732.2	688.4	645.8	607.8	572.2
145°	878.4	854.2	825.4	808.7	792.0	755.2	717.2	680.4	643.5	609.0	576.8
147.5°	831.2	813.9	790.9	778.8	766.7	735.6	704.5	672.3	640.1	609.0	580.2
150°	793.2	780.5	763.3	752.3	741.4	717.2	690.7	664.3	635.5	609.0	581.4
152.5°	762.1	750.6	737.9	729.3	720.7	699.9	678.1	655.0	629.7	605.5	583.7
155°	734.5	725.3	714.9	708.0	701.1	683.8	665.4	645.8	622.8	603.2	583.7
157.5°	709.2	702.2	693.0	687.2	681.5	667.7	651.6	635.5	617.1	599.8	584.8
160°	687.3	680.4	672.3	668.3	664.3	652.7	640.1	625.1	610.1	597.5	584.8
162.5°	664.3	658.5	653.9	650.4	647.0	636.6	626.3	614.8	603.2	592.9	583.7
165°	644.7	640.1	635.5	632.6	629.7	621.7	614.8	605.5	596.3	588.3	581.4
167.5°	625.1	621.7	619.4	617.1	614.8	610.1	604.4	596.3	589.4	583.7	580.2
170°	607.8	605.5	604.4	603.2	602.1	597.5	594.0	588.3	582.5	579.1	576.8
172.5°	594.0	591.7	591.7	591.2	590.6	587.1	584.8	580.2	576.8	575.6	575.6
175°	581.4	580.2	580.2	580.2	580.2	577.9	576.8	574.5	572.2	572.2	573.3
177.5°	573.3	572.2	573.3	573.3	573.3	572.2	571.0	569.9	568.7	569.9	572.2
180°	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6
2.5°	1621.6	1614.9	1608.2	1608.2	1593.5	1580.0	1573.3	1576.0	1568.0	1557.2	1546.5
5°	1692.7	1665.9	1660.5	1645.8	1625.6	1597.5	1582.7	1569.3	1553.2	1531.8	1511.6
7.5°	1758.4	1723.6	1704.8	1690.0	1651.1	1612.2	1580.0	1558.6	1530.4	1498.2	1474.1
10°	1844.3	1779.9	1759.8	1726.2	1671.3	1616.3	1578.7	1543.8	1504.9	1467.4	1435.2
12.5°	1912.7	1838.9	1801.4	1767.8	1696.7	1627.0	1563.9	1521.0	1474.1	1432.5	1390.9
15°	1990.5	1907.3	1841.6	1801.4	1711.5	1627.0	1555.9	1495.5	1443.2	1392.3	1356.0
17.5°	2028.0	1923.4	1893.9	1836.2	1706.1	1621.6	1534.4	1470.1	1407.0	1348.0	1305.1
20°	2087.1	1965.0	1891.2	1852.3	1737.0	1612.2	1510.3	1436.5	1370.8	1307.8	1262.2
22.5°	2091.1	1958.3	1910.0	1836.2	1694.1	1584.1	1488.8	1399.0	1322.5	1263.5	1216.6
25°	2081.7	1946.2	1879.2	1820.1	1702.1	1568.0	1445.9	1357.4	1282.3	1213.9	1158.9
27.5°	2077.7	1911.3	1848.3	1789.3	1656.5	1521.0	1420.4	1319.8	1234.0	1173.6	1117.3
30°	2072.3	1873.8	1797.3	1728.9	1606.9	1484.8	1364.1	1276.9	1195.1	1118.6	1062.3
32.5°	2037.4	1822.8	1745.0	1672.6	1541.1	1419.1	1323.9	1231.3	1142.8	1071.7	1020.7
35°	2026.7	1775.9	1673.9	1596.1	1467.4	1358.7	1258.1	1181.7	1098.5	1027.4	967.1
37.5°	1995.8	1727.6	1617.6	1518.3	1384.2	1280.9	1207.2	1130.7	1050.2	973.8	925.5
40°	1942.2	1671.3	1546.5	1444.6	1306.4	1201.8	1133.4	1077.1	997.9	929.5	870.5
42.5°	1863.1	1613.6	1479.4	1372.1	1219.2	1121.3	1065.0	1011.3	944.3	873.2	824.9
45°	1771.8	1537.1	1412.4	1293.0	1137.4	1042.2	983.2	951.0	889.3	828.9	772.6
47.5°	1647.1	1458.0	1334.6	1211.2	1052.9	960.4	913.4	881.2	838.3	772.6	727.0
50°	1490.2	1356.0	1239.4	1129.4	969.8	881.2	834.3	810.1	773.9	727.0	682.7
52.5°	1315.8	1238.0	1141.4	1039.5	885.3	802.1	759.2	740.4	713.6	669.3	631.7
55°	1140.1	1106.6	1040.8	940.2	796.7	728.3	690.8	666.6	646.5	614.3	582.1
57.5°	983.2	967.1	921.5	843.7	723.0	651.9	619.7	603.6	587.5	563.3	531.2
60°	820.9	838.3	791.4	752.5	642.5	580.8	552.6	535.2	527.1	505.7	485.5
62.5°	680.0	696.1	669.3	639.8	562.0	507.0	489.6	473.5	468.1	449.3	429.2
65°	552.6	572.7	552.6	536.5	489.6	444.0	422.5	414.5	409.1	397.0	380.9
67.5°	439.9	460.1	450.7	430.6	415.8	378.2	366.2	358.1	355.4	346.1	332.6
70°	331.3	359.5	362.1	350.1	336.7	319.2	311.2	308.5	301.8	293.7	285.7
72.5°	238.8	270.9	272.3	272.3	264.2	264.2	256.2	252.2	252.2	244.1	234.7
75°	175.7	197.2	199.9	202.5	206.6	210.6	205.2	205.2	203.9	195.8	191.8
77.5°	116.7	135.5	142.2	151.6	156.9	156.9	159.6	162.3	159.6	155.6	152.9
80°	75.1	88.5	96.6	101.9	110.0	114.0	118.0	119.4	116.7	115.4	111.3
82.5°	49.6	53.7	57.7	64.4	73.8	80.5	80.5	79.1	81.8	80.5	79.1
85°	28.2	30.8	32.2	33.5	38.9	45.6	46.9	48.3	51.0	48.3	45.6
87.5°	10.7	12.1	12.1	12.1	14.8	16.1	20.1	25.5	24.1	21.5	21.5
90°	18.4	15.0	13.8	12.7	10.4	6.9	4.6	2.3	4.6	6.9	10.4
92.5°	116.3	79.4	69.1	58.7	47.2	36.8	25.3	17.3	25.3	36.8	47.2
95°	247.5	149.7	127.2	104.8	74.8	55.3	42.6	39.1	42.6	55.3	74.8
97.5°	267.1	170.4	145.6	120.9	90.9	73.7	63.3	62.2	63.3	73.7	90.9
100°	263.6	183.0	160.6	138.1	110.5	94.4	86.3	85.2	86.3	94.4	110.5
102.5°	268.2	198.0	177.8	157.7	133.5	118.6	111.7	109.4	111.7	118.6	133.5
105°	277.4	215.3	197.4	179.6	157.7	143.9	137.0	133.5	137.0	143.9	157.7
107.5°	292.4	237.2	220.5	203.8	183.0	169.2	162.3	158.9	162.3	169.2	183.0
110°	312.0	260.2	244.0	227.9	208.4	195.7	190.0	186.5	190.0	195.7	208.4

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	331.6	284.4	268.8	253.3	233.7	221.0	215.3	211.8	215.3	221.0	233.7
115°	353.4	309.7	294.2	278.6	259.0	247.5	240.6	236.0	240.6	247.5	259.0
117.5°	376.4	332.7	318.3	303.9	282.0	271.7	265.9	260.2	265.9	271.7	282.0
120°	398.3	356.9	342.5	328.1	306.2	294.7	289.0	285.5	289.0	294.7	306.2
122.5°	421.3	381.1	365.6	350.0	329.2	316.6	310.8	307.4	310.8	316.6	329.2
125°	443.2	402.9	387.4	371.8	350.0	337.3	330.4	328.1	330.4	337.3	350.0
127.5°	462.8	423.7	408.2	392.6	368.4	355.7	347.7	344.2	347.7	355.7	368.4
130°	480.1	442.1	426.6	411.0	386.8	373.0	362.6	359.2	362.6	373.0	386.8
132.5°	495.0	458.2	443.2	428.3	404.1	386.8	375.3	370.7	375.3	386.8	404.1
135°	510.0	474.3	458.8	443.2	419.0	401.8	389.1	384.5	389.1	401.8	419.0
137.5°	520.4	485.8	471.4	457.0	432.9	414.4	401.8	397.2	401.8	414.4	432.9
140°	530.7	497.3	482.9	468.5	445.5	427.1	415.6	409.8	415.6	427.1	445.5
142.5°	538.8	506.5	493.3	480.1	457.0	440.9	428.3	423.7	428.3	440.9	457.0
145°	545.7	515.7	502.5	489.3	469.7	452.4	442.1	438.6	442.1	452.4	469.7
147.5°	551.4	523.8	512.3	500.8	481.2	466.2	455.9	453.6	455.9	466.2	481.2
150°	557.2	530.7	520.4	510.0	493.9	478.9	469.7	468.5	469.7	478.9	493.9
152.5°	560.6	538.8	529.0	519.2	505.4	492.7	483.5	483.5	483.5	492.7	505.4
155°	565.3	545.7	537.7	529.6	516.9	505.4	498.5	498.5	498.5	505.4	516.9
157.5°	567.6	551.4	545.1	538.8	527.3	516.9	511.1	510.0	511.1	516.9	527.3
160°	571.0	557.2	551.4	545.7	537.6	528.4	523.8	523.8	523.8	528.4	537.6
162.5°	572.2	560.6	556.0	551.4	544.5	537.6	534.2	534.2	534.2	537.6	544.5
165°	573.3	564.1	560.0	556.0	551.4	545.7	543.4	544.5	543.4	545.7	551.4
167.5°	573.3	566.4	563.5	560.6	557.2	552.6	551.4	552.6	551.4	552.6	557.2
170°	572.2	566.4	565.2	564.1	561.8	558.3	557.2	559.5	557.2	558.3	561.8
172.5°	572.2	567.6	567.0	566.4	565.3	562.9	562.9	564.1	562.9	562.9	565.3
175°	571.0	568.7	568.2	567.6	567.6	565.3	566.4	567.6	566.4	565.3	567.6
177.5°	569.9	568.7	568.7	568.7	568.7	567.6	568.7	569.9	568.7	567.6	568.7
180°	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6
2.5°	1546.5	1539.8	1537.1	1530.4	1514.3	1503.6	1491.5	1483.5	1484.8	1478.1	1482.1
5°	1498.2	1496.9	1487.5	1474.1	1451.3	1439.2	1417.7	1407.0	1401.7	1403.0	1394.9
7.5°	1458.0	1445.9	1439.2	1417.7	1396.3	1370.8	1353.4	1344.0	1335.9	1327.9	1322.5
10°	1412.4	1401.7	1390.9	1368.1	1338.6	1314.5	1290.3	1280.9	1268.9	1263.5	1259.5
12.5°	1364.1	1357.4	1344.0	1317.2	1283.6	1260.8	1232.6	1227.3	1211.2	1200.5	1197.8
15°	1319.8	1315.8	1291.7	1260.8	1227.3	1204.5	1180.3	1164.2	1137.4	1142.8	1133.4
17.5°	1272.9	1255.5	1240.7	1199.1	1183.0	1148.1	1120.0	1111.9	1093.2	1081.1	1069.0
20°	1220.6	1209.8	1191.1	1164.2	1125.3	1085.1	1063.6	1050.2	1039.5	1020.7	1015.4
22.5°	1171.0	1157.5	1141.4	1106.6	1073.0	1039.5	1010.0	997.9	984.5	971.1	963.0
25°	1132.1	1111.9	1094.5	1051.6	1018.0	989.9	971.1	951.0	932.2	924.2	921.5
27.5°	1071.7	1059.6	1042.2	1001.9	971.1	940.2	922.8	909.4	889.3	879.9	871.8
30°	1032.8	1008.7	988.5	956.3	925.5	892.0	875.9	859.8	847.7	835.6	826.2
32.5°	980.5	961.7	945.6	913.4	882.6	851.7	834.3	810.1	803.4	794.0	783.3
35°	929.5	917.4	900.0	865.1	831.6	810.1	791.4	768.6	760.5	753.8	744.4
37.5°	881.2	863.8	851.7	818.2	788.7	763.2	748.4	729.7	724.3	716.3	709.5
40°	839.7	822.2	810.1	776.6	745.8	718.9	709.5	690.8	682.7	673.3	669.3
42.5°	792.7	778.0	761.9	737.7	705.5	678.7	659.9	649.2	638.5	634.4	626.4
45°	743.1	729.7	717.6	690.8	657.2	638.5	622.4	607.6	599.6	592.9	587.5
47.5°	700.2	688.1	672.0	642.5	615.7	598.2	582.1	567.4	559.3	551.3	544.6
50°	650.5	643.8	626.4	598.2	572.7	552.6	537.9	524.4	519.1	509.7	499.0
52.5°	606.3	594.2	579.4	556.6	533.8	509.7	489.6	481.5	472.1	466.8	457.4
55°	554.0	545.9	529.8	509.7	485.5	465.4	450.7	439.9	427.9	422.5	410.4
57.5°	509.7	494.9	486.9	461.4	438.6	418.5	407.8	397.0	383.6	375.6	370.2
60°	461.4	448.0	435.9	414.5	398.4	376.9	360.8	351.4	342.0	331.3	325.9
62.5°	414.5	403.7	389.0	371.5	351.4	334.0	321.9	308.5	303.1	292.4	288.4
65°	363.5	355.4	343.4	323.3	307.2	292.4	280.3	269.6	264.2	260.2	257.5
67.5°	317.9	307.2	299.1	281.7	264.2	252.2	245.5	238.8	232.0	228.0	224.0
70°	270.9	262.9	254.8	238.8	226.7	215.9	210.6	205.2	201.2	197.2	193.1
72.5°	222.7	218.6	210.6	199.9	190.5	182.4	178.4	171.7	167.7	161.0	158.3
75°	183.8	177.1	173.0	163.6	155.6	148.9	143.5	135.5	130.1	127.4	126.1
77.5°	144.9	142.2	136.8	128.8	124.7	118.0	110.0	107.3	104.6	104.6	103.3
80°	108.6	104.6	100.6	93.9	89.9	84.5	84.5	84.5	83.2	84.5	83.2
82.5°	73.8	71.1	68.4	64.4	63.0	63.0	64.4	64.4	64.4	64.4	64.4
85°	42.9	42.9	42.9	44.3	42.9	42.9	44.3	45.6	44.3	44.3	42.9
87.5°	20.1	20.1	21.5	21.5	22.8	22.8	22.8	22.8	22.8	22.8	24.1
90°	12.7	13.8	15.0	18.4	21.9	25.3	28.8	27.6	28.8	29.9	31.1
92.5°	58.7	69.1	79.4	116.3	177.3	237.2	214.1	160.0	114.0	88.6	77.1
95°	104.8	127.2	149.7	247.5	419.0	607.8	682.7	553.7	414.4	280.9	219.9
97.5°	120.9	145.6	170.4	267.1	466.2	784.0	1049.9	1085.6	952.1	718.4	566.4
100°	138.1	160.6	183.0	263.6	434.0	736.8	1090.2	1317.0	1357.3	1264.0	1129.3
102.5°	157.7	177.8	198.0	268.2	406.4	667.7	1015.4	1328.5	1492.0	1511.6	1447.1
105°	179.6	197.4	215.3	277.4	396.0	613.6	925.6	1256.0	1496.6	1611.7	1633.6
107.5°	203.8	220.5	237.2	292.4	393.7	574.5	846.1	1152.4	1427.5	1608.3	1698.1
110°	227.9	244.0	260.2	312.0	399.5	553.7	780.5	1055.7	1319.3	1531.1	1676.2

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	253.3	268.8	284.4	331.6	411.0	542.2	736.8	971.6	1212.2	1429.8	1596.7
115°	278.6	294.2	309.7	353.4	423.7	541.1	708.0	907.2	1120.1	1320.5	1489.7
117.5°	303.9	318.3	332.7	376.4	439.8	542.2	688.4	864.6	1048.8	1226.1	1381.5
120°	328.1	342.5	356.9	398.3	458.2	546.8	675.8	832.3	994.7	1150.1	1288.2
122.5°	350.0	365.6	381.1	421.3	475.5	554.9	667.7	805.9	952.1	1089.1	1214.5
125°	371.8	387.4	402.9	443.2	493.9	562.9	660.8	784.0	915.2	1040.7	1151.2
127.5°	392.6	408.2	423.7	462.8	508.8	572.2	657.3	763.3	881.8	995.8	1097.1
130°	411.0	426.6	442.1	480.1	523.8	581.4	653.9	747.1	850.8	954.4	1047.6
132.5°	428.3	443.2	458.2	495.0	537.6	588.3	652.7	732.2	822.0	915.2	1000.4
135°	443.2	458.8	474.3	510.0	549.1	595.2	651.6	719.5	796.6	878.4	953.2
137.5°	457.0	471.4	485.8	520.4	558.3	599.8	649.3	708.0	772.5	841.5	908.3
140°	468.5	482.9	497.3	530.7	565.3	604.4	648.1	697.6	751.7	810.5	865.7
142.5°	480.1	493.3	506.5	538.8	572.2	607.8	645.8	688.4	732.2	780.5	826.6
145°	489.3	502.5	515.7	545.7	576.8	609.0	643.5	680.4	717.2	755.2	792.0
147.5°	500.8	512.3	523.8	551.4	580.2	609.0	640.1	672.3	704.5	735.6	766.7
150°	510.0	520.4	530.7	557.2	581.4	609.0	635.5	664.3	690.7	717.2	741.4
152.5°	519.2	529.0	538.8	560.6	583.7	605.5	629.7	655.0	678.1	699.9	720.7
155°	529.6	537.7	545.7	565.3	583.7	603.2	622.8	645.8	665.4	683.8	701.1
157.5°	538.8	545.1	551.4	567.6	584.8	599.8	617.1	635.5	651.6	667.7	681.5
160°	545.7	551.4	557.2	571.0	584.8	597.5	610.1	625.1	640.1	652.7	664.3
162.5°	551.4	556.0	560.6	572.2	583.7	592.9	603.2	614.8	626.3	636.6	647.0
165°	556.0	560.0	564.1	573.3	581.4	588.3	596.3	605.5	614.8	621.7	629.7
167.5°	560.6	563.5	566.4	573.3	580.2	583.7	589.4	596.3	604.4	610.1	614.8
170°	564.1	565.2	566.4	572.2	576.8	579.1	582.5	588.3	594.0	597.5	602.1
172.5°	566.4	567.0	567.6	572.2	575.6	575.6	576.8	580.2	584.8	587.1	590.6
175°	567.6	568.2	568.7	571.0	573.3	572.2	572.2	574.5	576.8	577.9	580.2
177.5°	568.7	568.7	568.7	569.9	572.2	569.9	568.7	569.9	571.0	572.2	573.3
180°	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6
2.5°	1480.8	1482.1	1478.1	1470.1	1468.7	1471.4	1479.4	1476.8	1470.1	1482.1	1471.4
5°	1399.0	1392.3	1389.6	1392.3	1384.2	1380.2	1388.2	1384.2	1388.2	1389.6	1393.6
7.5°	1319.8	1321.2	1313.1	1314.5	1303.7	1306.4	1306.4	1306.4	1310.4	1313.1	1318.5
10°	1251.4	1254.1	1244.7	1246.1	1238.0	1232.6	1236.7	1244.7	1244.7	1244.7	1247.4
12.5°	1196.4	1184.4	1177.7	1176.3	1166.9	1164.2	1172.3	1175.0	1181.7	1181.7	1185.7
15°	1128.0	1125.3	1120.0	1120.0	1097.2	1102.5	1105.2	1114.6	1128.0	1117.3	1120.0
17.5°	1066.3	1059.6	1052.9	1050.2	1047.6	1039.5	1050.2	1048.9	1056.9	1058.3	1062.3
20°	1011.3	1006.0	992.6	993.9	996.6	984.5	991.2	991.2	999.3	1007.3	1016.7
22.5°	957.7	952.3	945.6	948.3	940.2	937.6	937.6	944.3	953.7	960.4	959.0
25°	916.1	906.7	902.7	898.7	894.6	897.3	893.3	900.0	906.7	910.7	906.7
27.5°	869.2	865.1	857.1	853.1	846.4	849.0	851.7	857.1	861.1	861.1	865.1
30°	823.6	818.2	815.5	811.5	811.5	806.1	807.5	812.8	816.8	820.9	826.2
32.5°	779.3	775.3	771.2	771.2	768.6	767.2	765.9	773.9	773.9	782.0	782.0
35°	743.1	736.4	736.4	729.7	732.3	731.0	728.3	733.7	735.0	740.4	739.1
37.5°	702.8	702.8	700.2	693.4	688.1	689.4	696.1	696.1	700.2	698.8	702.8
40°	662.6	659.9	659.9	655.9	654.6	653.2	654.6	655.9	662.6	661.3	662.6
42.5°	622.4	623.7	617.0	617.0	617.0	613.0	614.3	615.7	618.3	621.0	625.0
45°	583.5	580.8	579.4	576.8	574.1	575.4	574.1	579.4	578.1	580.8	584.8
47.5°	541.9	537.9	536.5	531.2	531.2	533.8	532.5	536.5	537.9	541.9	539.2
50°	501.6	496.3	492.3	493.6	485.5	488.2	488.2	492.3	496.3	497.6	500.3
52.5°	454.7	453.4	452.0	445.3	444.0	442.6	444.0	445.3	450.7	454.7	456.0
55°	409.1	407.8	399.7	397.0	393.0	393.0	395.7	397.0	406.4	407.8	413.1
57.5°	367.5	363.5	354.1	352.8	352.8	352.8	348.7	354.1	356.8	363.5	363.5
60°	321.9	321.9	313.9	313.9	315.2	313.9	313.9	315.2	315.2	320.6	323.3
62.5°	285.7	284.4	284.4	281.7	280.3	281.7	280.3	280.3	281.7	285.7	289.7
65°	253.5	252.2	250.8	249.5	246.8	246.8	248.1	250.8	250.8	253.5	254.8
67.5°	222.7	222.7	220.0	220.0	218.6	217.3	218.6	217.3	222.7	222.7	224.0
70°	191.8	190.5	186.4	185.1	181.1	182.4	182.4	186.4	187.8	190.5	193.1
72.5°	154.2	154.2	151.6	148.9	150.2	147.5	147.5	148.9	148.9	152.9	154.2
75°	127.4	124.7	123.4	124.7	123.4	126.1	123.4	123.4	126.1	126.1	126.1
77.5°	104.6	104.6	103.3	103.3	104.6	103.3	104.6	104.6	104.6	103.3	104.6
80°	85.8	84.5	84.5	84.5	83.2	83.2	83.2	83.2	83.2	83.2	83.2
82.5°	64.4	64.4	63.0	64.4	64.4	63.0	64.4	63.0	63.0	64.4	64.4
85°	42.9	45.6	42.9	42.9	44.3	44.3	45.6	44.3	45.6	42.9	44.3
87.5°	22.8	24.1	24.1	22.8	22.8	24.1	24.1	24.1	25.5	22.8	24.1
90°	32.2	33.4	32.2	33.4	34.5	33.4	34.5	33.4	32.2	33.4	32.2
92.5°	73.1	69.1	66.8	62.2	63.3	61.0	63.3	62.2	66.8	69.1	73.1
95°	199.2	178.4	156.6	146.2	138.1	133.5	138.1	146.2	156.6	178.4	199.2
97.5°	500.8	435.2	358.0	314.3	286.7	274.0	286.7	314.3	358.0	435.2	500.8
100°	1047.6	965.9	849.6	765.6	720.7	721.8	720.7	765.6	849.6	965.9	1047.6
102.5°	1402.8	1358.4	1274.4	1212.2	1176.6	1143.2	1176.6	1212.2	1274.4	1358.4	1402.8
105°	1618.6	1603.7	1550.7	1507.0	1470.1	1464.4	1470.1	1507.0	1550.7	1603.7	1618.6
107.5°	1713.6	1729.1	1722.2	1701.5	1686.5	1673.9	1686.5	1701.5	1722.2	1729.1	1713.6
110°	1716.5	1756.8	1789.0	1798.2	1795.9	1793.6	1795.9	1798.2	1789.0	1756.8	1716.5

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1651.4	1706.1	1771.7	1805.1	1816.6	1817.8	1816.6	1805.1	1771.7	1706.1	1651.4
115°	1552.4	1615.2	1701.5	1752.2	1775.2	1780.9	1775.2	1752.2	1701.5	1615.2	1552.4
117.5°	1446.6	1511.6	1601.4	1657.8	1692.3	1700.4	1692.3	1657.8	1601.4	1511.6	1446.6
120°	1346.4	1404.5	1495.4	1559.9	1587.5	1594.4	1587.5	1559.9	1495.4	1404.5	1346.4
122.5°	1267.5	1320.5	1398.7	1455.1	1486.2	1495.4	1486.2	1455.1	1398.7	1320.5	1267.5
125°	1197.2	1243.3	1317.0	1367.7	1396.4	1404.5	1396.4	1367.7	1317.0	1243.3	1197.2
127.5°	1139.7	1182.3	1249.1	1292.8	1319.3	1326.2	1319.3	1292.8	1249.1	1182.3	1139.7
130°	1086.8	1125.9	1186.9	1228.4	1252.5	1261.7	1252.5	1228.4	1186.9	1125.9	1086.8
132.5°	1037.2	1074.1	1130.5	1171.9	1192.7	1198.4	1192.7	1171.9	1130.5	1074.1	1037.2
135°	986.0	1018.8	1075.2	1109.8	1130.5	1138.6	1130.5	1109.8	1075.2	1018.8	986.0
137.5°	937.6	967.0	1015.4	1051.1	1068.3	1075.2	1068.3	1051.1	1015.4	967.0	937.6
140°	890.4	915.2	959.0	991.2	1009.6	1008.5	1009.6	991.2	959.0	915.2	890.4
142.5°	847.3	868.0	903.7	931.3	947.5	946.3	947.5	931.3	903.7	868.0	847.3
145°	808.7	825.4	854.2	878.4	887.6	889.9	887.6	878.4	854.2	825.4	808.7
147.5°	778.8	790.9	813.9	831.2	840.4	841.5	840.4	831.2	813.9	790.9	778.8
150°	752.3	763.3	780.5	793.2	800.1	800.1	800.1	793.2	780.5	763.3	752.3
152.5°	729.3	737.9	750.6	762.1	765.6	765.6	765.6	762.1	750.6	737.9	729.3
155°	708.0	714.9	725.3	734.5	736.8	737.9	736.8	734.5	725.3	714.9	708.0
157.5°	687.2	693.0	702.2	709.2	711.5	711.5	711.5	709.2	702.2	693.0	687.2
160°	668.3	672.3	680.4	687.3	687.3	686.1	687.3	687.3	680.4	672.3	668.3
162.5°	650.4	653.9	658.5	664.3	664.3	663.1	664.3	664.3	658.5	653.9	650.4
165°	632.6	635.5	640.1	644.7	643.5	643.5	643.5	644.7	640.1	635.5	632.6
167.5°	617.1	619.4	621.7	625.1	624.0	624.0	624.0	625.1	621.7	619.4	617.1
170°	603.2	604.4	605.5	607.8	606.7	606.7	606.7	607.8	605.5	604.4	603.2
172.5°	591.2	591.7	591.7	594.0	591.7	590.6	591.7	594.0	591.7	591.7	591.2
175°	580.2	580.2	580.2	581.4	580.2	579.1	580.2	581.4	580.2	580.2	580.2
177.5°	573.3	573.3	572.2	573.3	571.0	571.0	571.0	573.3	572.2	573.3	573.3
180°	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6	1566.6
2.5°	1482.1	1487.5	1482.1	1471.4	1482.1	1488.8	1495.5	1506.3	1511.6	1511.6	1519.7
5°	1397.6	1408.4	1404.3	1401.7	1412.4	1419.1	1429.8	1443.2	1458.0	1467.4	1478.1
7.5°	1322.5	1329.2	1335.9	1335.9	1346.7	1361.4	1377.5	1393.6	1412.4	1425.8	1433.8
10°	1256.8	1262.2	1266.2	1271.5	1287.6	1303.7	1325.2	1345.3	1361.4	1376.2	1389.6
12.5°	1193.8	1201.8	1211.2	1215.2	1227.3	1247.4	1267.5	1291.7	1317.2	1331.9	1345.3
15°	1133.4	1137.4	1148.1	1160.2	1171.0	1192.4	1217.9	1243.4	1264.8	1287.6	1299.7
17.5°	1071.7	1073.0	1101.2	1094.5	1129.4	1149.5	1162.9	1187.0	1221.9	1240.7	1259.5
20°	1011.3	1024.7	1036.8	1043.5	1062.3	1085.1	1124.0	1142.8	1171.0	1188.4	1204.5
22.5°	964.4	984.5	984.5	1000.6	1010.0	1031.5	1059.6	1095.8	1126.7	1138.8	1161.6
25°	922.8	932.2	948.3	953.7	971.1	989.9	1008.7	1047.6	1081.1	1097.2	1113.3
27.5°	869.2	881.2	902.7	902.7	925.5	945.6	968.4	993.9	1027.4	1050.2	1067.7
30°	827.6	839.7	849.0	863.8	873.2	892.0	932.2	951.0	980.5	1000.6	1022.1
32.5°	788.7	798.1	806.1	822.2	832.9	854.4	875.9	909.4	934.9	953.7	976.5
35°	745.8	755.1	765.9	778.0	794.0	814.2	834.3	862.5	887.9	905.4	924.2
37.5°	705.5	712.2	728.3	736.4	749.8	768.6	794.0	823.6	846.4	859.8	878.5
40°	666.6	672.0	684.1	698.8	708.2	723.0	749.8	775.3	803.4	819.5	834.3
42.5°	625.0	631.7	642.5	657.2	672.0	688.1	702.8	732.3	757.8	771.2	787.3
45°	588.8	592.9	600.9	615.7	630.4	642.5	665.3	692.1	716.3	727.0	744.4
47.5°	545.9	549.9	562.0	568.7	584.8	600.9	623.7	650.5	672.0	682.7	698.8
50°	501.6	505.7	513.7	528.5	539.2	556.6	576.8	599.6	626.4	641.1	650.5
52.5°	458.7	466.8	473.5	485.5	499.0	516.4	535.2	556.6	579.4	594.2	604.9
55°	415.8	422.5	430.6	437.3	453.4	469.5	490.9	511.0	531.2	544.6	556.6
57.5°	367.5	376.9	385.0	398.4	410.4	423.8	448.0	464.1	488.2	497.6	508.4
60°	325.9	335.3	342.0	352.8	363.5	380.9	397.0	417.1	437.3	449.3	462.7
62.5°	291.1	295.1	299.1	309.8	320.6	336.7	352.8	372.9	394.3	401.0	411.8
65°	256.2	260.2	266.9	276.3	284.4	293.7	311.2	327.3	347.4	358.1	362.1
67.5°	226.7	230.7	232.0	238.8	245.5	256.2	265.6	281.7	300.4	307.2	315.2
70°	193.1	199.9	201.2	206.6	209.2	215.9	226.7	238.8	253.5	265.6	272.3
72.5°	154.2	163.6	166.3	174.4	178.4	185.1	193.1	202.5	211.9	217.3	222.7
75°	126.1	128.8	130.1	136.8	143.5	152.9	156.9	162.3	170.3	177.1	182.4
77.5°	104.6	106.0	107.3	107.3	108.6	114.0	122.1	128.8	134.1	136.8	140.8
80°	84.5	83.2	83.2	84.5	84.5	84.5	87.2	96.6	99.3	106.0	104.6
82.5°	65.7	63.0	64.4	63.0	63.0	63.0	63.0	64.4	64.4	68.4	71.1
85°	42.9	44.3	42.9	42.9	41.6	42.9	41.6	41.6	40.2	40.2	38.9
87.5°	22.8	24.1	22.8	22.8	21.5	22.8	21.5	21.5	20.1	20.1	17.4
90°	31.1	29.9	28.8	27.6	28.8	25.3	21.9	18.4	15.0	13.8	12.7
92.5°	77.1	88.6	114.0	160.0	214.1	237.2	177.3	116.3	79.4	69.1	58.7
95°	219.9	280.9	414.4	553.7	682.7	607.8	419.0	247.5	149.7	127.2	104.8
97.5°	566.4	718.4	952.1	1085.6	1049.9	784.0	466.2	267.1	170.4	145.6	120.9
100°	1129.3	1264.0	1357.3	1317.0	1090.2	736.8	434.0	263.6	183.0	160.6	138.1
102.5°	1447.1	1511.6	1492.0	1328.5	1015.4	667.7	406.4	268.2	198.0	177.8	157.7
105°	1633.6	1611.7	1496.6	1256.0	925.6	613.6	396.0	277.4	215.3	197.4	179.6
107.5°	1698.1	1608.3	1427.5	1152.4	846.1	574.5	393.7	292.4	237.2	220.5	203.8
110°	1676.2	1531.1	1319.3	1055.7	780.5	553.7	399.5	312.0	260.2	244.0	227.9

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1596.7	1429.8	1212.2	971.6	736.8	542.2	411.0	331.6	284.4	268.8	253.3
115°	1489.7	1320.5	1120.1	907.2	708.0	541.1	423.7	353.4	309.7	294.2	278.6
117.5°	1381.5	1226.1	1048.8	864.6	688.4	542.2	439.8	376.4	332.7	318.3	303.9
120°	1288.2	1150.1	994.7	832.3	675.8	546.8	458.2	398.3	356.9	342.5	328.1
122.5°	1214.5	1089.1	952.1	805.9	667.7	554.9	475.5	421.3	381.1	365.6	350.0
125°	1151.2	1040.7	915.2	784.0	660.8	562.9	493.9	443.2	402.9	387.4	371.8
127.5°	1097.1	995.8	881.8	763.3	657.3	572.2	508.8	462.8	423.7	408.2	392.6
130°	1047.6	954.4	850.8	747.1	653.9	581.4	523.8	480.1	442.1	426.6	411.0
132.5°	1000.4	915.2	822.0	732.2	652.7	588.3	537.6	495.0	458.2	443.2	428.3
135°	953.2	878.4	796.6	719.5	651.6	595.2	549.1	510.0	474.3	458.8	443.2
137.5°	908.3	841.5	772.5	708.0	649.3	599.8	558.3	520.4	485.8	471.4	457.0
140°	865.7	810.5	751.7	697.6	648.1	604.4	565.3	530.7	497.3	482.9	468.5
142.5°	826.6	780.5	732.2	688.4	645.8	607.8	572.2	538.8	506.5	493.3	480.1
145°	792.0	755.2	717.2	680.4	643.5	609.0	576.8	545.7	515.7	502.5	489.3
147.5°	766.7	735.6	704.5	672.3	640.1	609.0	580.2	551.4	523.8	512.3	500.8
150°	741.4	717.2	690.7	664.3	635.5	609.0	581.4	557.2	530.7	520.4	510.0
152.5°	720.7	699.9	678.1	655.0	629.7	605.5	583.7	560.6	538.8	529.0	519.2
155°	701.1	683.8	665.4	645.8	622.8	603.2	583.7	565.3	545.7	537.7	529.6
157.5°	681.5	667.7	651.6	635.5	617.1	599.8	584.8	567.6	551.4	545.1	538.8
160°	664.3	652.7	640.1	625.1	610.1	597.5	584.8	571.0	557.2	551.4	545.7
162.5°	647.0	636.6	626.3	614.8	603.2	592.9	583.7	572.2	560.6	556.0	551.4
165°	629.7	621.7	614.8	605.5	596.3	588.3	581.4	573.3	564.1	560.0	556.0
167.5°	614.8	610.1	604.4	596.3	589.4	583.7	580.2	573.3	566.4	563.5	560.6
170°	602.1	597.5	594.0	588.3	582.5	579.1	576.8	572.2	566.4	565.2	564.1
172.5°	590.6	587.1	584.8	580.2	576.8	575.6	575.6	572.2	567.6	567.0	566.4
175°	580.2	577.9	576.8	574.5	572.2	572.2	573.3	571.0	568.7	568.2	567.6
177.5°	573.3	572.2	571.0	569.9	568.7	569.9	572.2	569.9	568.7	568.7	568.7
180°	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7	568.7

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1566.6	1566.6	1566.6	1566.6
2.5°	1526.4	1535.8	1554.6	1570.7
5°	1494.2	1509.0	1537.1	1565.3
7.5°	1455.3	1478.1	1514.3	1553.2
10°	1417.7	1447.3	1491.5	1537.1
12.5°	1380.2	1411.0	1458.0	1517.0
15°	1335.9	1368.1	1424.5	1495.5
17.5°	1297.0	1340.0	1390.9	1462.0
20°	1255.5	1287.6	1353.4	1428.5
22.5°	1203.1	1256.8	1318.5	1397.6
25°	1161.6	1208.5	1270.2	1360.1
27.5°	1110.6	1165.6	1240.7	1319.8
30°	1069.0	1114.6	1184.4	1279.6
32.5°	1020.7	1074.4	1146.8	1240.7
35°	977.8	1023.4	1091.8	1187.0
37.5°	926.8	976.5	1052.9	1137.4
40°	882.6	930.9	1003.3	1082.4
42.5°	828.9	879.9	952.3	1019.4
45°	786.0	832.9	890.6	952.3
47.5°	733.7	783.3	839.7	882.6
50°	686.7	732.3	776.6	812.8
52.5°	635.8	677.4	717.6	744.4
55°	588.8	621.0	653.2	672.0
57.5°	533.8	564.7	591.5	602.2
60°	485.5	511.0	528.5	540.5
62.5°	434.6	453.4	466.8	473.5
65°	385.0	398.4	405.1	411.8
67.5°	334.0	346.1	350.1	358.1
70°	280.3	293.7	296.4	300.4
72.5°	240.1	240.1	245.5	250.8
75°	191.8	194.5	197.2	197.2
77.5°	150.2	150.2	152.9	154.2
80°	110.0	111.3	111.3	110.0
82.5°	75.1	77.8	75.1	73.8
85°	41.6	46.9	44.3	44.3
87.5°	17.4	17.4	20.1	17.4
90°	10.4	6.9	4.6	2.3
92.5°	47.2	36.8	25.3	17.3
95°	74.8	55.3	42.6	39.1
97.5°	90.9	73.7	63.3	62.2
100°	110.5	94.4	86.3	85.2
102.5°	133.5	118.6	111.7	109.4
105°	157.7	143.9	137.0	133.5
107.5°	183.0	169.2	162.3	158.9
110°	208.4	195.7	190.0	186.5

TEST NUMBER: P1012146

CATALOG NUMBER: S123RDIP-B1000D1195UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	233.7	221.0	215.3	211.8
115°	259.0	247.5	240.6	236.0
117.5°	282.0	271.7	265.9	260.2
120°	306.2	294.7	289.0	285.5
122.5°	329.2	316.6	310.8	307.4
125°	350.0	337.3	330.4	328.1
127.5°	368.4	355.7	347.7	344.2
130°	386.8	373.0	362.6	359.2
132.5°	404.1	386.8	375.3	370.7
135°	419.0	401.8	389.1	384.5
137.5°	432.9	414.4	401.8	397.2
140°	445.5	427.1	415.6	409.8
142.5°	457.0	440.9	428.3	423.7
145°	469.7	452.4	442.1	438.6
147.5°	481.2	466.2	455.9	453.6
150°	493.9	478.9	469.7	468.5
152.5°	505.4	492.7	483.5	483.5
155°	516.9	505.4	498.5	498.5
157.5°	527.3	516.9	511.1	510.0
160°	537.6	528.4	523.8	523.8
162.5°	544.5	537.6	534.2	534.2
165°	551.4	545.7	543.4	544.5
167.5°	557.2	552.6	551.4	552.6
170°	561.8	558.3	557.2	559.5
172.5°	565.3	562.9	562.9	564.1
175°	567.6	565.3	566.4	567.6
177.5°	568.7	567.6	568.7	569.9
180°	568.7	568.7	568.7	568.7

(END OF REPORT)