

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012152

Luminaire Tested: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012152
REPORT IS A COMBINATION OF REPORTS P992777 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8253.0 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	94	90	87	90	86	83	80	73	71	69	60	59	57	49	48	47
2	90	82	77	72	82	76	71	67	64	61	58	54	51	49	43	42	40
3	82	73	66	60	75	68	61	57	57	53	49	48	45	42	39	37	35
4	75	65	57	52	69	60	54	48	51	46	42	43	39	36	35	33	30
5	69	58	50	45	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	29	26	24
7	59	47	40	34	54	44	37	32	38	33	29	32	28	25	27	24	21
8	55	43	36	30	51	40	33	29	35	29	26	30	25	22	25	22	19
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17010	17010	17010	17010
5°	17023	19591	17067	14534
10°	16873	23649	16947	12695
15°	16699	26840	16699	11194
20°	16356	28951	16448	9930
25°	16106	27505	16074	9060
30°	15814	19058	15781	8210
35°	15464	12236	15394	7570
40°	15027	8640	14952	6932
45°	14266	6914	14247	6311
50°	13333	5784	13289	5585
55°	12281	4767	12183	4734
60°	11252	3940	11138	4026
65°	10042	3153	10107	3412
70°	8926	2191	9164	2759
75°	7566	1625	7874	2122
80°	6021	1077	6536	1591
85°	4284	510	4678	989

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 22709 cd/sqm

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.2	1.9
10°-20°	485.8	5.9
20°-30°	765.1	9.3
30°-40°	795.6	9.6
40°-50°	680.7	8.2
50°-60°	518.9	6.3
60°-70°	332.5	4.0
70°-80°	159.3	1.9
80°-90°	45.1	0.5
90°-100°	311.3	3.8
100°-110°	911.3	11.0
110°-120°	889.9	10.8
120°-130°	708.7	8.6
130°-140°	559.2	6.8
140°-150°	417.1	5.1
150°-160°	290.9	3.5
160°-170°	170.9	2.1
170°-180°	55.6	0.7
0°-30°	1406.1	17.0
0°-40°	2201.7	26.7
0°-60°	3401.4	41.2
0°-90°	3938.2	47.7
90°-120°	2112.5	25.6
90°-150°	3797.6	46.0
90°-180°	4315.0	52.3
0°-180°	8253.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1580	1580	1580	1580	1580	
5°	1579	1877	1583	1392	1579	150
15°	1509	2667	1509	1112	1509	424
25°	1372	2748	1369	905	1372	632
35°	1197	1192	1192	737	1197	749
45°	961	636	959	580	961	740
55°	678	399	672	396	678	607
65°	415	230	418	249	415	415
75°	199	97	207	127	199	215
85°	45	23	49	45	45	50
90°	2	34	2	34	2	5
95°	40	135	40	135	40	42
105°	135	1477	135	1477	135	143
115°	238	1796	238	1796	238	236
125°	331	1417	331	1417	331	294
135°	388	1148	388	1148	388	300
145°	442	898	442	898	442	277
155°	503	744	503	744	503	231
165°	549	649	549	649	549	155
175°	572	584	572	584	572	54
180°	574	574	574	574	574	

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3
2.5°	1584.3	1595.2	1603.3	1608.7	1622.2	1630.3	1637.1	1649.3	1649.3	1652.0	1657.4
5°	1578.9	1601.9	1618.2	1639.8	1668.2	1681.8	1700.7	1716.9	1739.9	1752.1	1764.3
7.5°	1566.8	1599.2	1633.1	1665.5	1707.5	1734.5	1753.5	1795.4	1825.2	1861.7	1890.1
10°	1550.5	1595.2	1638.5	1688.5	1745.4	1785.9	1814.4	1869.8	1926.7	1978.1	2021.4
12.5°	1530.2	1584.3	1646.6	1707.5	1787.3	1827.9	1873.9	1942.9	2024.1	2089.0	2147.2
15°	1508.6	1570.8	1641.2	1715.6	1815.7	1872.5	1938.8	2022.7	2113.4	2206.7	2286.5
17.5°	1474.8	1553.2	1631.7	1739.9	1857.6	1891.5	1948.3	2063.3	2175.6	2259.5	2356.9
20°	1440.9	1528.9	1627.6	1725.1	1852.2	1930.7	1983.5	2105.2	2225.7	2327.1	2420.5
22.5°	1409.8	1501.8	1604.6	1727.8	1846.8	1925.3	1991.6	2118.8	2258.1	2371.8	2486.8
25°	1371.9	1472.0	1585.7	1702.1	1846.8	1906.4	1979.4	2126.9	2274.4	2405.6	2547.7
27.5°	1331.3	1432.8	1545.1	1664.2	1796.8	1884.7	1956.4	2114.7	2294.7	2435.4	2581.5
30°	1290.7	1394.9	1503.2	1610.1	1758.9	1842.8	1925.3	2099.8	2305.5	2466.5	2578.8
32.5°	1251.5	1339.5	1446.3	1550.5	1698.0	1790.0	1883.4	2084.9	2309.5	2444.8	2499.0
35°	1197.4	1289.4	1376.0	1486.9	1635.8	1726.4	1836.0	2083.6	2292.0	2375.8	2348.8
37.5°	1147.3	1224.5	1307.0	1405.8	1558.6	1676.3	1790.0	2048.4	2233.8	2239.2	2086.3
40°	1091.9	1155.4	1224.5	1328.6	1493.7	1610.1	1733.2	1994.3	2128.2	2048.4	1779.2
42.5°	1028.3	1085.1	1139.2	1240.7	1420.6	1550.5	1683.1	1926.7	1975.4	1791.4	1511.3
45°	960.6	1006.6	1056.7	1163.6	1343.5	1472.0	1604.6	1822.5	1772.4	1512.6	1246.1
47.5°	890.3	929.5	978.2	1075.6	1261.0	1392.2	1518.0	1673.6	1546.5	1267.7	1044.5
50°	819.9	851.0	898.4	998.5	1177.1	1296.2	1412.5	1514.0	1335.4	1087.8	863.2
52.5°	750.9	775.3	824.0	909.2	1082.4	1196.0	1279.9	1319.2	1137.9	898.4	749.6
55°	677.8	704.9	737.4	824.0	995.8	1079.7	1135.2	1133.8	947.1	761.7	619.7
57.5°	607.5	631.8	660.3	746.8	886.2	943.0	990.4	967.4	790.1	623.7	531.7
60°	545.3	558.8	589.9	663.0	768.5	817.2	844.3	805.0	645.4	526.3	439.7
62.5°	477.6	491.1	516.8	585.8	650.8	676.5	699.5	649.4	533.1	428.9	376.1
65°	415.4	433.0	449.2	504.7	539.8	571.0	568.3	526.3	416.7	349.1	305.8
67.5°	361.2	368.0	381.5	415.4	431.6	454.6	456.0	408.6	335.5	284.1	258.4
70°	303.1	309.8	319.3	335.5	346.4	351.8	349.1	307.1	253.0	221.9	198.9
72.5°	253.0	251.7	258.4	258.4	269.2	267.9	259.8	227.3	192.1	166.4	152.9
75°	198.9	200.2	201.6	198.9	194.8	189.4	182.7	158.3	135.3	123.1	110.9
77.5°	155.6	152.9	154.2	144.8	139.4	133.9	124.5	112.3	93.4	90.6	85.2
80°	110.9	109.6	108.2	104.2	92.0	86.6	79.8	73.1	69.0	66.3	64.9
82.5°	74.4	74.4	71.7	63.6	56.8	52.8	51.4	48.7	44.6	44.6	43.3
85°	44.6	43.3	40.6	32.5	28.4	28.4	28.4	28.4	25.7	25.7	24.4
87.5°	17.6	16.2	12.2	12.2	10.8	10.8	10.8	9.5	9.5	8.1	8.1
90°	2.3	4.6	7.0	10.5	12.8	14.0	15.1	18.6	22.1	25.5	29.0
92.5°	17.4	25.5	37.2	47.6	59.2	69.6	80.1	117.3	178.8	239.2	216.0
95°	39.5	43.0	55.7	75.5	105.7	128.4	151.0	249.7	422.7	613.1	688.6
97.5°	62.7	63.9	74.3	91.7	121.9	146.9	171.9	269.4	470.3	790.8	1059.0
100°	85.9	87.1	95.2	111.5	139.3	162.0	184.6	265.9	437.8	743.2	1099.6
102.5°	110.3	112.6	119.6	134.7	159.1	179.4	199.7	270.6	409.9	673.5	1024.2
105°	134.7	138.2	145.1	159.1	181.1	199.1	217.1	279.8	399.4	618.9	933.6
107.5°	160.2	163.7	170.7	184.6	205.5	222.4	239.2	294.9	397.1	579.4	853.5
110°	188.1	191.6	197.4	210.2	229.9	246.2	262.4	314.7	402.9	558.5	787.3

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	213.7	217.1	222.9	235.7	255.5	271.2	286.8	334.4	414.5	546.9	743.2
115°	238.0	242.7	249.7	261.3	281.0	296.7	312.4	356.5	427.3	545.8	714.1
117.5°	262.4	268.2	274.0	284.5	306.5	321.0	335.6	379.7	443.6	546.9	694.4
120°	288.0	291.5	297.3	308.9	330.9	345.4	360.0	401.8	462.1	551.6	681.6
122.5°	310.0	313.5	319.3	332.1	353.0	368.6	384.3	425.0	479.6	559.7	673.5
125°	330.9	333.3	340.2	353.0	375.1	390.8	406.4	447.1	498.1	567.8	666.5
127.5°	347.2	350.7	358.8	371.6	396.0	411.6	427.3	466.8	513.2	577.1	663.0
130°	362.3	365.8	376.2	390.2	414.5	430.2	445.9	484.2	528.3	586.4	659.5
132.5°	373.9	378.5	390.2	407.6	432.0	447.0	462.1	499.3	542.3	593.4	658.4
135°	387.8	392.5	405.2	422.7	447.1	462.8	478.4	514.4	553.9	600.3	657.2
137.5°	400.6	405.2	418.0	436.6	461.0	475.5	490.0	524.9	563.2	605.0	654.9
140°	413.4	419.2	430.8	449.4	472.6	487.1	501.6	535.3	570.1	609.6	653.7
142.5°	427.3	432.0	444.7	461.0	484.2	497.6	510.9	543.4	577.1	613.1	651.4
145°	442.4	445.9	456.3	473.8	493.5	506.8	520.2	550.4	581.7	614.3	649.1
147.5°	457.5	459.8	470.3	485.4	505.1	516.7	528.3	556.2	585.2	614.3	645.6
150°	472.6	473.8	483.0	498.1	514.4	524.8	535.3	562.0	586.4	614.3	641.0
152.5°	487.7	487.7	497.0	509.8	523.7	533.6	543.4	565.5	588.7	610.8	635.2
155°	502.8	502.8	509.8	521.4	534.1	542.2	550.4	570.1	588.7	608.5	628.2
157.5°	514.4	515.6	521.4	531.8	543.4	549.8	556.2	572.5	589.9	605.0	622.4
160°	528.3	528.3	533.0	542.3	550.4	556.2	562.0	575.9	589.9	602.6	615.4
162.5°	538.8	538.8	542.3	549.2	556.2	560.8	565.5	577.1	588.7	598.0	608.5
165°	549.2	548.1	550.4	556.2	560.8	564.9	569.0	578.3	586.4	593.4	601.5
167.5°	557.4	556.2	557.4	562.0	565.5	568.4	571.3	578.3	585.2	588.7	594.5
170°	564.3	562.0	563.2	566.7	569.0	570.2	571.3	577.1	581.7	584.1	587.6
172.5°	569.0	567.8	567.8	570.1	571.3	571.9	572.5	577.1	580.6	580.6	581.7
175°	572.5	571.3	570.1	572.5	572.5	573.0	573.6	575.9	578.3	577.1	577.1
177.5°	574.8	573.6	572.5	573.6	573.6	573.6	573.6	574.8	577.1	574.8	573.6
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3
2.5°	1668.2	1668.2	1680.4	1692.6	1685.8	1689.9	1704.8	1699.3	1710.2	1708.8	1712.9
5°	1794.1	1808.9	1821.1	1846.8	1850.9	1846.8	1872.5	1879.3	1891.5	1876.6	1883.4
7.5°	1936.1	1967.2	1997.0	2034.9	2047.1	2049.8	2063.3	2082.2	2098.5	2068.7	2083.6
10°	2074.1	2121.5	2182.4	2216.2	2246.0	2256.8	2267.6	2279.8	2298.7	2316.3	2302.8
12.5°	2223.0	2292.0	2350.1	2411.0	2447.5	2443.5	2474.6	2482.7	2497.6	2501.7	2507.1
15°	2344.7	2442.1	2478.7	2569.3	2577.4	2604.5	2639.7	2670.8	2674.9	2666.7	2666.7
17.5°	2461.1	2545.0	2609.9	2683.0	2697.9	2720.9	2765.5	2780.4	2785.8	2784.4	2784.4
20°	2555.8	2611.3	2720.9	2781.7	2806.1	2835.9	2867.0	2885.9	2890.0	2895.4	2887.3
22.5°	2618.0	2701.9	2791.2	2841.3	2861.6	2872.4	2892.7	2898.1	2891.3	2892.7	2894.0
25°	2666.7	2749.3	2803.4	2816.9	2815.6	2802.0	2787.1	2761.4	2758.7	2747.9	2726.3
27.5°	2680.3	2711.4	2704.6	2649.1	2593.7	2588.3	2499.0	2450.3	2394.8	2402.9	2371.8
30°	2607.2	2566.6	2470.6	2329.8	2271.7	2177.0	2076.8	1972.7	1932.1	1887.4	1969.9
32.5°	2428.6	2283.8	2113.4	1930.7	1833.3	1749.4	1642.5	1566.8	1523.5	1486.9	1557.3
35°	2159.4	1933.4	1707.5	1534.3	1454.5	1378.7	1278.6	1240.7	1186.6	1192.0	1198.7
37.5°	1813.0	1564.1	1393.6	1223.1	1170.3	1139.2	1066.2	1008.0	989.0	983.6	983.6
40°	1488.3	1284.0	1132.4	998.5	957.9	932.2	874.0	847.0	826.7	821.3	828.0
42.5°	1231.2	1056.7	939.0	849.7	821.3	788.8	764.4	730.6	726.6	717.1	729.3
45°	1033.7	882.1	794.2	729.3	704.9	692.7	665.7	645.4	637.3	635.9	645.4
47.5°	876.7	759.0	681.9	641.3	622.4	610.2	587.2	579.1	571.0	573.7	569.6
50°	736.0	648.1	598.0	561.5	549.3	537.1	522.3	514.1	510.1	510.1	508.7
52.5°	631.8	558.8	526.3	492.5	487.1	480.3	464.1	458.7	451.9	450.5	456.0
55°	541.2	491.1	458.7	438.4	433.0	419.4	412.7	405.9	401.8	399.1	400.5
57.5°	462.7	424.8	403.2	385.6	376.1	370.7	358.5	357.2	354.5	354.5	353.1
60°	397.8	370.7	345.0	334.2	327.4	320.7	319.3	311.2	307.1	309.8	308.5
62.5°	336.9	315.2	300.4	288.2	284.1	278.7	274.7	271.9	267.9	269.2	269.2
65°	281.4	263.8	253.0	242.2	240.8	235.4	234.1	231.4	231.4	230.0	232.7
67.5°	231.4	219.2	209.7	202.9	198.9	200.2	194.8	190.8	190.8	189.4	193.5
70°	184.0	177.2	167.8	159.7	154.2	154.2	147.5	146.1	146.1	146.1	144.8
72.5°	142.1	129.9	125.8	123.1	123.1	123.1	120.4	120.4	119.1	120.4	119.1
75°	105.5	104.2	101.5	100.1	100.1	98.8	97.4	97.4	97.4	97.4	97.4
77.5°	82.5	82.5	79.8	78.5	78.5	78.5	77.1	77.1	75.8	75.8	75.8
80°	60.9	60.9	58.2	58.2	58.2	56.8	56.8	56.8	58.2	56.8	56.8
82.5°	41.9	41.9	40.6	41.9	40.6	39.2	39.2	39.2	37.9	39.2	39.2
85°	24.4	24.4	23.0	21.6	23.0	23.0	21.6	23.0	21.6	23.0	21.6
87.5°	9.5	8.1	8.1	8.1	6.8	8.1	6.8	6.8	8.1	6.8	8.1
90°	27.9	29.0	30.2	31.4	32.6	33.7	32.5	33.7	34.8	33.7	34.8
92.5°	161.4	115.0	89.4	77.8	73.8	69.7	67.3	62.7	63.9	61.5	63.9
95°	558.5	418.0	283.3	221.8	200.9	180.0	157.9	147.5	139.3	134.7	139.3
97.5°	1095.0	960.3	724.6	571.3	505.1	438.9	361.1	317.0	289.1	276.4	289.1
100°	1328.4	1369.0	1275.0	1139.1	1056.6	974.2	856.9	772.2	726.9	728.1	726.9
102.5°	1340.0	1504.9	1524.6	1459.6	1414.9	1370.2	1285.4	1222.7	1186.7	1153.0	1186.7
105°	1266.8	1509.5	1625.6	1647.7	1632.6	1617.5	1564.1	1520.0	1482.8	1477.0	1482.8
107.5°	1162.3	1439.9	1622.2	1712.7	1728.4	1744.1	1737.1	1716.2	1701.1	1688.3	1701.1
110°	1064.8	1330.7	1544.4	1690.7	1731.4	1772.0	1804.5	1813.8	1811.4	1809.1	1811.4

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	980.0	1222.7	1442.2	1610.5	1665.7	1720.9	1787.0	1820.7	1832.3	1833.5	1832.3
115°	915.0	1129.8	1331.9	1502.6	1565.8	1629.1	1716.2	1767.3	1790.5	1796.3	1790.5
117.5°	872.0	1057.8	1236.6	1393.4	1459.0	1524.6	1615.2	1672.1	1706.9	1715.1	1706.9
120°	839.5	1003.3	1160.0	1299.4	1358.0	1416.6	1508.4	1573.4	1601.3	1608.2	1601.3
122.5°	812.8	960.3	1098.5	1225.0	1278.4	1331.9	1410.8	1467.7	1499.1	1508.4	1499.1
125°	790.8	923.1	1049.7	1161.2	1207.6	1254.1	1328.4	1379.5	1408.5	1416.6	1408.5
127.5°	769.9	889.5	1004.4	1106.6	1149.6	1192.5	1259.9	1304.0	1330.7	1337.7	1330.7
130°	753.6	858.1	962.6	1056.7	1096.2	1135.6	1197.2	1239.0	1263.4	1272.6	1263.4
132.5°	738.5	829.1	923.1	1009.1	1046.2	1083.4	1140.3	1182.1	1203.0	1208.8	1203.0
135°	725.7	803.5	886.0	961.5	994.6	1027.6	1084.5	1119.4	1140.3	1148.4	1140.3
137.5°	714.1	779.1	848.8	916.2	945.8	975.4	1024.2	1060.2	1077.6	1084.5	1077.6
140°	703.7	758.2	817.5	873.2	898.2	923.1	967.3	999.8	1018.3	1017.2	1018.3
142.5°	694.4	738.5	787.3	833.7	854.6	875.5	911.5	939.4	955.6	954.5	955.6
145°	686.3	723.4	761.7	798.9	815.8	832.6	861.6	886.0	895.3	897.6	895.3
147.5°	678.1	710.6	742.0	773.3	785.5	797.7	820.9	838.4	847.7	848.8	847.7
150°	670.0	696.7	723.4	747.8	758.8	769.9	787.3	800.0	807.0	807.0	807.0
152.5°	660.7	683.9	706.0	726.9	735.6	744.3	757.1	768.7	772.2	772.2	772.2
155°	651.4	671.2	689.7	707.2	714.2	721.1	731.5	740.8	743.2	744.3	743.2
157.5°	641.0	657.2	673.5	687.4	693.2	699.0	708.3	715.3	717.6	717.6	717.6
160°	630.5	645.6	658.4	670.0	674.0	678.1	686.3	693.2	693.2	692.1	693.2
162.5°	620.1	631.7	642.1	652.6	656.0	659.5	664.2	670.0	670.0	668.8	670.0
165°	610.8	620.1	627.0	635.2	638.1	641.0	645.6	650.3	649.1	649.1	649.1
167.5°	601.5	609.6	615.4	620.1	622.4	624.7	627.0	630.5	629.4	629.4	629.4
170°	593.4	599.2	602.6	607.3	608.4	609.6	610.8	613.1	611.9	611.9	611.9
172.5°	585.2	589.9	592.2	595.7	596.2	596.8	596.8	599.2	596.8	595.7	596.8
175°	579.4	581.7	582.9	585.2	585.2	585.2	585.2	586.4	585.2	584.1	585.2
177.5°	574.8	575.9	577.1	578.3	578.3	578.3	577.1	578.3	575.9	575.9	575.9
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3
2.5°	1706.1	1698.0	1692.6	1688.5	1684.5	1696.6	1680.4	1662.8	1650.6	1642.5	1639.8
5°	1884.7	1867.1	1852.2	1840.1	1842.8	1842.8	1814.4	1783.2	1756.2	1741.3	1725.1
7.5°	2091.7	2072.8	2043.0	2036.2	2030.8	1997.0	1968.6	1911.8	1877.9	1844.1	1814.4
10°	2297.4	2273.0	2244.6	2235.1	2221.6	2179.7	2136.4	2063.3	2021.4	1959.1	1919.9
12.5°	2489.5	2459.7	2431.3	2424.5	2404.3	2367.7	2293.3	2217.5	2145.8	2079.5	2010.5
15°	2650.5	2642.4	2599.1	2572.0	2527.4	2477.3	2461.1	2358.3	2267.6	2198.6	2074.1
17.5°	2785.8	2747.9	2707.3	2689.7	2672.1	2614.0	2555.8	2450.3	2352.8	2251.4	2171.5
20°	2894.0	2852.1	2823.7	2798.0	2789.9	2723.6	2631.6	2538.2	2431.3	2317.7	2213.5
22.5°	2899.4	2894.0	2875.1	2860.2	2844.0	2800.7	2727.6	2611.3	2497.6	2373.1	2236.5
25°	2787.1	2779.0	2833.2	2819.6	2830.4	2814.2	2775.0	2677.6	2545.0	2398.8	2260.8
27.5°	2448.9	2531.4	2616.7	2646.4	2666.7	2724.9	2743.9	2689.7	2582.8	2427.3	2273.0
30°	1988.9	2098.5	2236.5	2310.9	2367.7	2476.0	2616.7	2634.3	2584.2	2459.7	2270.3
32.5°	1561.3	1661.5	1772.4	1860.4	1936.1	2158.0	2347.4	2484.1	2508.4	2443.5	2277.1
35°	1258.3	1301.6	1407.1	1491.0	1593.8	1783.2	2006.5	2227.0	2375.8	2384.0	2256.8
37.5°	1037.7	1060.7	1152.7	1200.1	1261.0	1427.4	1635.8	1923.9	2155.3	2264.9	2200.0
40°	859.1	911.9	964.7	991.7	1035.0	1150.0	1350.3	1576.2	1863.1	2066.0	2112.0
42.5°	745.5	768.5	802.3	840.2	867.3	967.4	1101.3	1308.3	1566.8	1849.5	1976.7
45°	657.6	665.7	700.8	725.2	753.6	824.0	918.7	1091.9	1319.2	1597.9	1814.4
47.5°	584.5	600.7	619.7	634.5	653.5	707.6	788.8	914.6	1114.9	1363.8	1596.5
50°	519.5	529.0	553.4	560.1	573.7	611.5	673.8	769.8	934.9	1133.8	1374.6
52.5°	458.7	476.3	485.7	495.2	507.4	538.5	579.1	657.6	782.0	968.7	1173.0
55°	411.3	416.7	430.2	438.4	447.8	469.5	504.7	562.8	660.3	809.1	1002.6
57.5°	365.3	365.3	378.8	385.6	395.1	411.3	442.4	487.1	557.4	668.4	845.6
60°	316.6	318.0	328.8	336.9	339.6	355.8	381.5	416.7	470.8	552.0	696.8
62.5°	273.3	280.1	285.5	288.2	297.7	307.1	328.8	353.1	391.0	462.7	565.5
65°	236.8	238.1	242.2	244.9	248.9	259.8	276.0	292.2	324.7	377.5	461.4
67.5°	194.8	200.2	205.7	205.7	209.7	215.1	231.4	244.9	269.2	300.4	357.2
70°	146.1	148.8	156.9	161.0	166.4	175.9	184.0	192.1	211.1	234.1	277.4
72.5°	121.8	121.8	124.5	125.8	125.8	132.6	144.8	152.9	162.4	178.6	208.4
75°	97.4	97.4	101.5	100.1	102.8	105.5	106.9	112.3	117.7	129.9	147.5
77.5°	77.1	78.5	78.5	79.8	79.8	81.2	82.5	85.2	87.9	94.7	102.8
80°	56.8	58.2	58.2	59.5	59.5	60.9	62.2	63.6	66.3	69.0	73.1
82.5°	39.2	40.6	40.6	41.9	40.6	41.9	43.3	43.3	44.6	47.4	48.7
85°	23.0	23.0	24.4	23.0	23.0	23.0	24.4	24.4	25.7	29.8	29.8
87.5°	6.8	8.1	6.8	8.1	8.1	8.1	8.1	9.5	9.5	10.8	12.2
90°	33.7	32.5	33.7	32.6	31.4	30.2	29.0	27.9	29.0	25.5	22.1
92.5°	62.7	67.3	69.7	73.8	77.8	89.4	115.0	161.4	216.0	239.2	178.8
95°	147.5	157.9	180.0	200.9	221.8	283.3	418.0	558.5	688.6	613.1	422.7
97.5°	317.0	361.1	438.9	505.1	571.3	724.6	960.3	1095.0	1059.0	790.8	470.3
100°	772.2	856.9	974.2	1056.6	1139.1	1275.0	1369.0	1328.4	1099.6	743.2	437.8
102.5°	1222.7	1285.4	1370.2	1414.9	1459.6	1524.6	1504.9	1340.0	1024.2	673.5	409.9
105°	1520.0	1564.1	1617.5	1632.6	1647.7	1625.6	1509.5	1266.8	933.6	618.9	399.4
107.5°	1716.2	1737.1	1744.1	1728.4	1712.7	1622.2	1439.9	1162.3	853.5	579.4	397.1
110°	1813.8	1804.5	1772.0	1731.4	1690.7	1544.4	1330.7	1064.8	787.3	558.5	402.9

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1820.7	1787.0	1720.9	1665.7	1610.5	1442.2	1222.7	980.0	743.2	546.9	414.5
115°	1767.3	1716.2	1629.1	1565.8	1502.6	1331.9	1129.8	915.0	714.1	545.8	427.3
117.5°	1672.1	1615.2	1524.6	1459.0	1393.4	1236.6	1057.8	872.0	694.4	546.9	443.6
120°	1573.4	1508.4	1416.6	1358.0	1299.4	1160.0	1003.3	839.5	681.6	551.6	462.1
122.5°	1467.7	1410.8	1331.9	1278.4	1225.0	1098.5	960.3	812.8	673.5	559.7	479.6
125°	1379.5	1328.4	1254.1	1207.6	1161.2	1049.7	923.1	790.8	666.5	567.8	498.1
127.5°	1304.0	1259.9	1192.5	1149.6	1106.6	1004.4	889.5	769.9	663.0	577.1	513.2
130°	1239.0	1197.2	1135.6	1096.2	1056.7	962.6	858.1	753.6	659.5	586.4	528.3
132.5°	1182.1	1140.3	1083.4	1046.2	1009.1	923.1	829.1	738.5	658.4	593.4	542.3
135°	1119.4	1084.5	1027.6	994.6	961.5	886.0	803.5	725.7	657.2	600.3	553.9
137.5°	1060.2	1024.2	975.4	945.8	916.2	848.8	779.1	714.1	654.9	605.0	563.2
140°	999.8	967.3	923.1	898.2	873.2	817.5	758.2	703.7	653.7	609.6	570.1
142.5°	939.4	911.5	875.5	854.6	833.7	787.3	738.5	694.4	651.4	613.1	577.1
145°	886.0	861.6	832.6	815.8	798.9	761.7	723.4	686.3	649.1	614.3	581.7
147.5°	838.4	820.9	797.7	785.5	773.3	742.0	710.6	678.1	645.6	614.3	585.2
150°	800.0	787.3	769.9	758.8	747.8	723.4	696.7	670.0	641.0	614.3	586.4
152.5°	768.7	757.1	744.3	735.6	726.9	706.0	683.9	660.7	635.2	610.8	588.7
155°	740.8	731.5	721.1	714.2	707.2	689.7	671.2	651.4	628.2	608.5	588.7
157.5°	715.3	708.3	699.0	693.2	687.4	673.5	657.2	641.0	622.4	605.0	589.9
160°	693.2	686.3	678.1	674.0	670.0	658.4	645.6	630.5	615.4	602.6	589.9
162.5°	670.0	664.2	659.5	656.0	652.6	642.1	631.7	620.1	608.5	598.0	588.7
165°	650.3	645.6	641.0	638.1	635.2	627.0	620.1	610.8	601.5	593.4	586.4
167.5°	630.5	627.0	624.7	622.4	620.1	615.4	609.6	601.5	594.5	588.7	585.2
170°	613.1	610.8	609.6	608.4	607.3	602.6	599.2	593.4	587.6	584.1	581.7
172.5°	599.2	596.8	596.8	596.2	595.7	592.2	589.9	585.2	581.7	580.6	580.6
175°	586.4	585.2	585.2	585.2	585.2	582.9	581.7	579.4	577.1	577.1	578.3
177.5°	578.3	577.1	578.3	578.3	578.3	577.1	575.9	574.8	573.6	574.8	577.1
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3
2.5°	1635.8	1629.0	1622.2	1622.2	1607.3	1593.8	1587.1	1589.8	1581.6	1570.8	1560.0
5°	1707.5	1680.4	1675.0	1660.1	1639.8	1611.4	1596.5	1583.0	1566.8	1545.1	1524.8
7.5°	1773.8	1738.6	1719.6	1704.8	1665.5	1626.3	1593.8	1572.2	1543.8	1511.3	1486.9
10°	1860.4	1795.4	1775.1	1741.3	1685.8	1630.3	1592.5	1557.3	1518.0	1480.2	1447.7
12.5°	1929.4	1854.9	1817.1	1783.2	1711.5	1641.2	1577.6	1534.3	1486.9	1445.0	1403.0
15°	2007.8	1923.9	1857.6	1817.1	1726.4	1641.2	1569.5	1508.6	1455.8	1404.4	1367.9
17.5°	2045.7	1940.2	1910.4	1852.2	1721.0	1635.8	1547.8	1482.9	1419.3	1359.7	1316.5
20°	2105.2	1982.1	1907.7	1868.5	1752.1	1626.3	1523.5	1449.0	1382.8	1319.2	1273.2
22.5°	2109.3	1975.4	1926.7	1852.2	1708.8	1597.9	1501.8	1411.2	1334.0	1274.5	1227.2
25°	2099.8	1963.2	1895.5	1836.0	1716.9	1581.6	1458.5	1369.2	1293.5	1224.5	1169.0
27.5°	2095.8	1928.0	1864.4	1804.9	1670.9	1534.3	1432.8	1331.3	1244.7	1183.9	1127.0
30°	2090.4	1890.1	1813.0	1744.0	1620.9	1497.8	1376.0	1288.0	1205.5	1128.4	1071.6
32.5°	2055.2	1838.7	1760.2	1687.2	1554.6	1431.5	1335.4	1242.0	1152.7	1081.0	1029.6
35°	2044.4	1791.4	1688.5	1610.1	1480.2	1370.6	1269.1	1192.0	1108.1	1036.4	975.5
37.5°	2013.2	1742.6	1631.7	1531.6	1396.3	1292.1	1217.7	1140.6	1059.4	982.3	933.6
40°	1959.1	1685.8	1560.0	1457.2	1317.8	1212.3	1143.3	1086.4	1006.6	937.6	878.1
42.5°	1879.3	1627.6	1492.3	1384.1	1229.9	1131.1	1074.3	1020.2	952.5	880.8	832.1
45°	1787.3	1550.5	1424.7	1304.3	1147.3	1051.3	991.7	959.3	897.0	836.1	779.3
47.5°	1661.5	1470.7	1346.2	1221.7	1062.1	968.7	921.4	888.9	845.6	779.3	733.3
50°	1503.2	1367.9	1250.2	1139.2	978.2	888.9	841.6	817.2	780.7	733.3	688.7
52.5°	1327.3	1248.8	1151.4	1048.6	893.0	809.1	765.8	746.8	719.8	675.1	637.3
55°	1150.0	1116.2	1049.9	948.4	803.7	734.7	696.8	672.4	652.1	619.7	587.2
57.5°	991.7	975.5	929.5	851.0	729.3	657.6	625.1	608.8	592.6	568.3	535.8
60°	828.0	845.6	798.3	759.0	648.1	585.8	557.4	539.8	531.7	510.1	489.8
62.5°	686.0	702.2	675.1	645.4	566.9	511.4	493.8	477.6	472.2	453.2	433.0
65°	557.4	577.7	557.4	541.2	493.8	447.8	426.2	418.1	412.7	400.5	384.2
67.5°	443.8	464.1	454.6	434.3	419.4	381.5	369.4	361.2	358.5	349.1	335.5
70°	334.2	362.6	365.3	353.1	339.6	322.0	313.9	311.2	304.4	296.3	288.2
72.5°	240.8	273.3	274.7	274.7	266.5	266.5	258.4	254.4	254.4	246.2	236.8
75°	177.2	198.9	201.6	204.3	208.4	212.4	207.0	207.0	205.7	197.5	193.5
77.5°	117.7	136.7	143.4	152.9	158.3	158.3	161.0	163.7	161.0	156.9	154.2
80°	75.8	89.3	97.4	102.8	110.9	115.0	119.1	120.4	117.7	116.4	112.3
82.5°	50.1	54.1	58.2	64.9	74.4	81.2	81.2	79.8	82.5	81.2	79.8
85°	28.4	31.1	32.5	33.8	39.2	46.0	47.4	48.7	51.4	48.7	46.0
87.5°	10.8	12.2	12.2	12.2	14.9	16.2	20.3	25.7	24.4	21.6	21.6
90°	18.6	15.1	14.0	12.8	10.5	7.0	4.6	2.3	4.6	7.0	10.5
92.5°	117.3	80.1	69.6	59.2	47.6	37.2	25.5	17.4	25.5	37.2	47.6
95°	249.7	151.0	128.4	105.7	75.5	55.7	43.0	39.5	43.0	55.7	75.5
97.5°	269.4	171.9	146.9	121.9	91.7	74.3	63.9	62.7	63.9	74.3	91.7
100°	265.9	184.6	162.0	139.3	111.5	95.2	87.1	85.9	87.1	95.2	111.5
102.5°	270.6	199.7	179.4	159.1	134.7	119.6	112.6	110.3	112.6	119.6	134.7
105°	279.8	217.1	199.1	181.1	159.1	145.1	138.2	134.7	138.2	145.1	159.1
107.5°	294.9	239.2	222.4	205.5	184.6	170.7	163.7	160.2	163.7	170.7	184.6
110°	314.7	262.4	246.2	229.9	210.2	197.4	191.6	188.1	191.6	197.4	210.2

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	334.4	286.8	271.2	255.5	235.7	222.9	217.1	213.7	217.1	222.9	235.7
115°	356.5	312.4	296.7	281.0	261.3	249.7	242.7	238.0	242.7	249.7	261.3
117.5°	379.7	335.6	321.0	306.5	284.5	274.0	268.2	262.4	268.2	274.0	284.5
120°	401.8	360.0	345.4	330.9	308.9	297.3	291.5	288.0	291.5	297.3	308.9
122.5°	425.0	384.3	368.6	353.0	332.1	319.3	313.5	310.0	313.5	319.3	332.1
125°	447.1	406.4	390.8	375.1	353.0	340.2	333.3	330.9	333.3	340.2	353.0
127.5°	466.8	427.3	411.6	396.0	371.6	358.8	350.7	347.2	350.7	358.8	371.6
130°	484.2	445.9	430.2	414.5	390.2	376.2	365.8	362.3	365.8	376.2	390.2
132.5°	499.3	462.1	447.0	432.0	407.6	390.2	378.5	373.9	378.5	390.2	407.6
135°	514.4	478.4	462.8	447.1	422.7	405.2	392.5	387.8	392.5	405.2	422.7
137.5°	524.9	490.0	475.5	461.0	436.6	418.0	405.2	400.6	405.2	418.0	436.6
140°	535.3	501.6	487.1	472.6	449.4	430.8	419.2	413.4	419.2	430.8	449.4
142.5°	543.4	510.9	497.6	484.2	461.0	444.7	432.0	427.3	432.0	444.7	461.0
145°	550.4	520.2	506.8	493.5	473.8	456.3	445.9	442.4	445.9	456.3	473.8
147.5°	556.2	528.3	516.7	505.1	485.4	470.3	459.8	457.5	459.8	470.3	485.4
150°	562.0	535.3	524.8	514.4	498.1	483.0	473.8	472.6	473.8	483.0	498.1
152.5°	565.5	543.4	533.6	523.7	509.8	497.0	487.7	487.7	487.7	497.0	509.8
155°	570.1	550.4	542.2	534.1	521.4	509.8	502.8	502.8	502.8	509.8	521.4
157.5°	572.5	556.2	549.8	543.4	531.8	521.4	515.6	514.4	515.6	521.4	531.8
160°	575.9	562.0	556.2	550.4	542.3	533.0	528.3	528.3	528.3	533.0	542.3
162.5°	577.1	565.5	560.8	556.2	549.2	542.3	538.8	538.8	538.8	542.3	549.2
165°	578.3	569.0	564.9	560.8	556.2	550.4	548.1	549.2	548.1	550.4	556.2
167.5°	578.3	571.3	568.4	565.5	562.0	557.4	556.2	557.4	556.2	557.4	562.0
170°	577.1	571.3	570.2	569.0	566.7	563.2	562.0	564.3	562.0	563.2	566.7
172.5°	577.1	572.5	571.9	571.3	570.1	567.8	567.8	569.0	567.8	567.8	570.1
175°	575.9	573.6	573.0	572.5	572.5	570.1	571.3	572.5	571.3	570.1	572.5
177.5°	574.8	573.6	573.6	573.6	573.6	572.5	573.6	574.8	573.6	572.5	573.6
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3
2.5°	1560.0	1553.2	1550.5	1543.8	1527.5	1516.7	1504.5	1496.4	1497.8	1491.0	1495.0
5°	1511.3	1509.9	1500.5	1486.9	1463.9	1451.8	1430.1	1419.3	1413.9	1415.2	1407.1
7.5°	1470.7	1458.5	1451.8	1430.1	1408.5	1382.8	1365.2	1355.7	1347.6	1339.5	1334.0
10°	1424.7	1413.9	1403.0	1380.0	1350.3	1325.9	1301.6	1292.1	1279.9	1274.5	1270.5
12.5°	1376.0	1369.2	1355.7	1328.6	1294.8	1271.8	1243.4	1238.0	1221.7	1210.9	1208.2
15°	1331.3	1327.3	1302.9	1271.8	1238.0	1215.0	1190.6	1174.4	1147.3	1152.7	1143.3
17.5°	1284.0	1266.4	1251.5	1209.6	1193.3	1158.2	1129.7	1121.6	1102.7	1090.5	1078.3
20°	1231.2	1220.4	1201.5	1174.4	1135.2	1094.6	1072.9	1059.4	1048.6	1029.6	1024.2
22.5°	1181.2	1167.6	1151.4	1116.2	1082.4	1048.6	1018.8	1006.6	993.1	979.6	971.4
25°	1141.9	1121.6	1104.0	1060.7	1026.9	998.5	979.6	959.3	940.3	932.2	929.5
27.5°	1081.0	1068.9	1051.3	1010.7	979.6	948.4	930.9	917.3	897.0	887.6	879.4
30°	1041.8	1017.4	997.1	964.7	933.6	899.7	883.5	867.3	855.1	842.9	833.4
32.5°	989.0	970.1	953.9	921.4	890.3	859.1	841.6	817.2	810.4	801.0	790.1
35°	937.6	925.4	907.9	872.7	838.9	817.2	798.3	775.3	767.1	760.4	750.9
37.5°	888.9	871.3	859.1	825.3	795.6	769.8	755.0	736.0	730.6	722.5	715.7
40°	847.0	829.4	817.2	783.4	752.3	725.2	715.7	696.8	688.7	679.2	675.1
42.5°	799.6	784.7	768.5	744.1	711.7	684.6	665.7	654.8	644.0	640.0	631.8
45°	749.6	736.0	723.8	696.8	663.0	644.0	627.8	612.9	604.8	598.0	592.6
47.5°	706.3	694.1	677.8	648.1	621.0	603.4	587.2	572.3	564.2	556.1	549.3
50°	656.2	649.4	631.8	603.4	577.7	557.4	542.5	529.0	523.6	514.1	503.3
52.5°	611.5	599.4	584.5	561.5	538.5	514.1	493.8	485.7	476.3	470.8	461.4
55°	558.8	550.7	534.4	514.1	489.8	469.5	454.6	443.8	431.6	426.2	414.0
57.5°	514.1	499.3	491.1	465.4	442.4	422.1	411.3	400.5	387.0	378.8	373.4
60°	465.4	451.9	439.7	418.1	401.8	380.2	364.0	354.5	345.0	334.2	328.8
62.5°	418.1	407.2	392.4	374.8	354.5	336.9	324.7	311.2	305.8	295.0	290.9
65°	366.7	358.5	346.4	326.1	309.8	295.0	282.8	271.9	266.5	262.5	259.8
67.5°	320.7	309.8	301.7	284.1	266.5	254.4	247.6	240.8	234.1	230.0	225.9
70°	273.3	265.2	257.1	240.8	228.7	217.8	212.4	207.0	202.9	198.9	194.8
72.5°	224.6	220.5	212.4	201.6	192.1	184.0	179.9	173.2	169.1	162.4	159.7
75°	185.4	178.6	174.5	165.1	156.9	150.2	144.8	136.7	131.2	128.5	127.2
77.5°	146.1	143.4	138.0	129.9	125.8	119.1	110.9	108.2	105.5	105.5	104.2
80°	109.6	105.5	101.5	94.7	90.6	85.2	85.2	85.2	83.9	85.2	83.9
82.5°	74.4	71.7	69.0	64.9	63.6	63.6	64.9	64.9	64.9	64.9	64.9
85°	43.3	43.3	43.3	44.6	43.3	43.3	44.6	46.0	44.6	44.6	43.3
87.5°	20.3	20.3	21.6	21.6	23.0	23.0	23.0	23.0	23.0	23.0	24.4
90°	12.8	14.0	15.1	18.6	22.1	25.5	29.0	27.9	29.0	30.2	31.4
92.5°	59.2	69.6	80.1	117.3	178.8	239.2	216.0	161.4	115.0	89.4	77.8
95°	105.7	128.4	151.0	249.7	422.7	613.1	688.6	558.5	418.0	283.3	221.8
97.5°	121.9	146.9	171.9	269.4	470.3	790.8	1059.0	1095.0	960.3	724.6	571.3
100°	139.3	162.0	184.6	265.9	437.8	743.2	1099.6	1328.4	1369.0	1275.0	1139.1
102.5°	159.1	179.4	199.7	270.6	409.9	673.5	1024.2	1340.0	1504.9	1524.6	1459.6
105°	181.1	199.1	217.1	279.8	399.4	618.9	933.6	1266.8	1509.5	1625.6	1647.7
107.5°	205.5	222.4	239.2	294.9	397.1	579.4	853.5	1162.3	1439.9	1622.2	1712.7
110°	229.9	246.2	262.4	314.7	402.9	558.5	787.3	1064.8	1330.7	1544.4	1690.7

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	255.5	271.2	286.8	334.4	414.5	546.9	743.2	980.0	1222.7	1442.2	1610.5
115°	281.0	296.7	312.4	356.5	427.3	545.8	714.1	915.0	1129.8	1331.9	1502.6
117.5°	306.5	321.0	335.6	379.7	443.6	546.9	694.4	872.0	1057.8	1236.6	1393.4
120°	330.9	345.4	360.0	401.8	462.1	551.6	681.6	839.5	1003.3	1160.0	1299.4
122.5°	353.0	368.6	384.3	425.0	479.6	559.7	673.5	812.8	960.3	1098.5	1225.0
125°	375.1	390.8	406.4	447.1	498.1	567.8	666.5	790.8	923.1	1049.7	1161.2
127.5°	396.0	411.6	427.3	466.8	513.2	577.1	663.0	769.9	889.5	1004.4	1106.6
130°	414.5	430.2	445.9	484.2	528.3	586.4	659.5	753.6	858.1	962.6	1056.7
132.5°	432.0	447.0	462.1	499.3	542.3	593.4	658.4	738.5	829.1	923.1	1009.1
135°	447.1	462.8	478.4	514.4	553.9	600.3	657.2	725.7	803.5	886.0	961.5
137.5°	461.0	475.5	490.0	524.9	563.2	605.0	654.9	714.1	779.1	848.8	916.2
140°	472.6	487.1	501.6	535.3	570.1	609.6	653.7	703.7	758.2	817.5	873.2
142.5°	484.2	497.6	510.9	543.4	577.1	613.1	651.4	694.4	738.5	787.3	833.7
145°	493.5	506.8	520.2	550.4	581.7	614.3	649.1	686.3	723.4	761.7	798.9
147.5°	505.1	516.7	528.3	556.2	585.2	614.3	645.6	678.1	710.6	742.0	773.3
150°	514.4	524.8	535.3	562.0	586.4	614.3	641.0	670.0	696.7	723.4	747.8
152.5°	523.7	533.6	543.4	565.5	588.7	610.8	635.2	660.7	683.9	706.0	726.9
155°	534.1	542.2	550.4	570.1	588.7	608.5	628.2	651.4	671.2	689.7	707.2
157.5°	543.4	549.8	556.2	572.5	589.9	605.0	622.4	641.0	657.2	673.5	687.4
160°	550.4	556.2	562.0	575.9	589.9	602.6	615.4	630.5	645.6	658.4	670.0
162.5°	556.2	560.8	565.5	577.1	588.7	598.0	608.5	620.1	631.7	642.1	652.6
165°	560.8	564.9	569.0	578.3	586.4	593.4	601.5	610.8	620.1	627.0	635.2
167.5°	565.5	568.4	571.3	578.3	585.2	588.7	594.5	601.5	609.6	615.4	620.1
170°	569.0	570.2	571.3	577.1	581.7	584.1	587.6	593.4	599.2	602.6	607.3
172.5°	571.3	571.9	572.5	577.1	580.6	580.6	581.7	585.2	589.9	592.2	595.7
175°	572.5	573.0	573.6	575.9	578.3	577.1	577.1	579.4	581.7	582.9	585.2
177.5°	573.6	573.6	573.6	574.8	577.1	574.8	573.6	574.8	575.9	577.1	578.3
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3
2.5°	1493.7	1495.0	1491.0	1482.9	1481.5	1484.2	1492.3	1489.6	1482.9	1495.0	1484.2
5°	1411.2	1404.4	1401.7	1404.4	1396.3	1392.2	1400.3	1396.3	1400.3	1401.7	1405.8
7.5°	1331.3	1332.7	1324.6	1325.9	1315.1	1317.8	1317.8	1317.8	1321.9	1324.6	1330.0
10°	1262.3	1265.0	1255.6	1256.9	1248.8	1243.4	1247.5	1255.6	1255.6	1255.6	1258.3
12.5°	1206.9	1194.7	1187.9	1186.6	1177.1	1174.4	1182.5	1185.2	1192.0	1192.0	1196.0
15°	1137.9	1135.2	1129.7	1129.7	1106.7	1112.2	1114.9	1124.3	1137.9	1127.0	1129.7
17.5°	1075.6	1068.9	1062.1	1059.4	1056.7	1048.6	1059.4	1058.0	1066.2	1067.5	1071.6
20°	1020.2	1014.7	1001.2	1002.6	1005.3	993.1	999.9	999.9	1008.0	1016.1	1025.6
22.5°	966.0	960.6	953.9	956.6	948.4	945.7	945.7	952.5	962.0	968.7	967.4
25°	924.1	914.6	910.6	906.5	902.4	905.1	901.1	907.9	914.6	918.7	914.6
27.5°	876.7	872.7	864.6	860.5	853.7	856.4	859.1	864.6	868.6	868.6	872.7
30°	830.7	825.3	822.6	818.6	818.6	813.1	814.5	819.9	824.0	828.0	833.4
32.5°	786.1	782.0	778.0	778.0	775.3	773.9	772.6	780.7	780.7	788.8	788.8
35°	749.6	742.8	742.8	736.0	738.7	737.4	734.7	740.1	741.4	746.8	745.5
37.5°	709.0	709.0	706.3	699.5	694.1	695.4	702.2	702.2	706.3	704.9	709.0
40°	668.4	665.7	665.7	661.6	660.3	658.9	660.3	661.6	668.4	667.0	668.4
42.5°	627.8	629.1	622.4	622.4	622.4	618.3	619.7	621.0	623.7	626.4	630.5
45°	588.5	585.8	584.5	581.8	579.1	580.4	579.1	584.5	583.1	585.8	589.9
47.5°	546.6	542.5	541.2	535.8	535.8	538.5	537.1	541.2	542.5	546.6	543.9
50°	506.0	500.6	496.5	497.9	489.8	492.5	492.5	496.5	500.6	502.0	504.7
52.5°	458.7	457.3	456.0	449.2	447.8	446.5	447.8	449.2	454.6	458.7	460.0
55°	412.7	411.3	403.2	400.5	396.4	396.4	399.1	400.5	410.0	411.3	416.7
57.5°	370.7	366.7	357.2	355.8	355.8	355.8	351.8	357.2	359.9	366.7	366.7
60°	324.7	324.7	316.6	316.6	318.0	316.6	316.6	318.0	318.0	323.4	326.1
62.5°	288.2	286.8	286.8	284.1	282.8	284.1	282.8	282.8	284.1	288.2	292.2
65°	255.7	254.4	253.0	251.7	248.9	248.9	250.3	253.0	253.0	255.7	257.1
67.5°	224.6	224.6	221.9	221.9	220.5	219.2	220.5	219.2	224.6	224.6	225.9
70°	193.5	192.1	188.1	186.7	182.7	184.0	184.0	188.1	189.4	192.1	194.8
72.5°	155.6	155.6	152.9	150.2	151.5	148.8	148.8	150.2	150.2	154.2	155.6
75°	128.5	125.8	124.5	125.8	124.5	127.2	124.5	124.5	127.2	127.2	127.2
77.5°	105.5	105.5	104.2	104.2	105.5	104.2	105.5	105.5	105.5	104.2	105.5
80°	86.6	85.2	85.2	85.2	83.9	83.9	83.9	83.9	83.9	83.9	83.9
82.5°	64.9	64.9	63.6	64.9	64.9	63.6	64.9	63.6	63.6	64.9	64.9
85°	43.3	46.0	43.3	43.3	44.6	44.6	46.0	44.6	46.0	43.3	44.6
87.5°	23.0	24.4	24.4	23.0	23.0	24.4	24.4	24.4	25.7	23.0	24.4
90°	32.6	33.7	32.5	33.7	34.8	33.7	34.8	33.7	32.5	33.7	32.6
92.5°	73.8	69.7	67.3	62.7	63.9	61.5	63.9	62.7	67.3	69.7	73.8
95°	200.9	180.0	157.9	147.5	139.3	134.7	139.3	147.5	157.9	180.0	200.9
97.5°	505.1	438.9	361.1	317.0	289.1	276.4	289.1	317.0	361.1	438.9	505.1
100°	1056.6	974.2	856.9	772.2	726.9	728.1	726.9	772.2	856.9	974.2	1056.6
102.5°	1414.9	1370.2	1285.4	1222.7	1186.7	1153.0	1186.7	1222.7	1285.4	1370.2	1414.9
105°	1632.6	1617.5	1564.1	1520.0	1482.8	1477.0	1482.8	1520.0	1564.1	1617.5	1632.6
107.5°	1728.4	1744.1	1737.1	1716.2	1701.1	1688.3	1701.1	1716.2	1737.1	1744.1	1728.4
110°	1731.4	1772.0	1804.5	1813.8	1811.4	1809.1	1811.4	1813.8	1804.5	1772.0	1731.4

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1665.7	1720.9	1787.0	1820.7	1832.3	1833.5	1832.3	1820.7	1787.0	1720.9	1665.7
115°	1565.8	1629.1	1716.2	1767.3	1790.5	1796.3	1790.5	1767.3	1716.2	1629.1	1565.8
117.5°	1459.0	1524.6	1615.2	1672.1	1706.9	1715.1	1706.9	1672.1	1615.2	1524.6	1459.0
120°	1358.0	1416.6	1508.4	1573.4	1601.3	1608.2	1601.3	1573.4	1508.4	1416.6	1358.0
122.5°	1278.4	1331.9	1410.8	1467.7	1499.1	1508.4	1499.1	1467.7	1410.8	1331.9	1278.4
125°	1207.6	1254.1	1328.4	1379.5	1408.5	1416.6	1408.5	1379.5	1328.4	1254.1	1207.6
127.5°	1149.6	1192.5	1259.9	1304.0	1330.7	1337.7	1330.7	1304.0	1259.9	1192.5	1149.6
130°	1096.2	1135.6	1197.2	1239.0	1263.4	1272.6	1263.4	1239.0	1197.2	1135.6	1096.2
132.5°	1046.2	1083.4	1140.3	1182.1	1203.0	1208.8	1203.0	1182.1	1140.3	1083.4	1046.2
135°	994.6	1027.6	1084.5	1119.4	1140.3	1148.4	1140.3	1119.4	1084.5	1027.6	994.6
137.5°	945.8	975.4	1024.2	1060.2	1077.6	1084.5	1077.6	1060.2	1024.2	975.4	945.8
140°	898.2	923.1	967.3	999.8	1018.3	1017.2	1018.3	999.8	967.3	923.1	898.2
142.5°	854.6	875.5	911.5	939.4	955.6	954.5	955.6	939.4	911.5	875.5	854.6
145°	815.8	832.6	861.6	886.0	895.3	897.6	895.3	886.0	861.6	832.6	815.8
147.5°	785.5	797.7	820.9	838.4	847.7	848.8	847.7	838.4	820.9	797.7	785.5
150°	758.8	769.9	787.3	800.0	807.0	807.0	807.0	800.0	787.3	769.9	758.8
152.5°	735.6	744.3	757.1	768.7	772.2	772.2	772.2	768.7	757.1	744.3	735.6
155°	714.2	721.1	731.5	740.8	743.2	744.3	743.2	740.8	731.5	721.1	714.2
157.5°	693.2	699.0	708.3	715.3	717.6	717.6	717.6	715.3	708.3	699.0	693.2
160°	674.0	678.1	686.3	693.2	693.2	692.1	693.2	693.2	686.3	678.1	674.0
162.5°	656.0	659.5	664.2	670.0	670.0	668.8	670.0	670.0	664.2	659.5	656.0
165°	638.1	641.0	645.6	650.3	649.1	649.1	649.1	650.3	645.6	641.0	638.1
167.5°	622.4	624.7	627.0	630.5	629.4	629.4	629.4	630.5	627.0	624.7	622.4
170°	608.4	609.6	610.8	613.1	611.9	611.9	611.9	613.1	610.8	609.6	608.4
172.5°	596.2	596.8	596.8	599.2	596.8	595.7	596.8	599.2	596.8	596.8	596.2
175°	585.2	585.2	585.2	586.4	585.2	584.1	585.2	586.4	585.2	585.2	585.2
177.5°	578.3	578.3	577.1	578.3	575.9	575.9	575.9	578.3	577.1	578.3	578.3
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3
2.5°	1495.0	1500.5	1495.0	1484.2	1495.0	1501.8	1508.6	1519.4	1524.8	1524.8	1532.9
5°	1409.8	1420.6	1416.6	1413.9	1424.7	1431.5	1442.3	1455.8	1470.7	1480.2	1491.0
7.5°	1334.0	1340.8	1347.6	1347.6	1358.4	1373.3	1389.5	1405.8	1424.7	1438.2	1446.3
10°	1267.7	1273.2	1277.2	1282.6	1298.9	1315.1	1336.7	1357.0	1373.3	1388.2	1401.7
12.5°	1204.2	1212.3	1221.7	1225.8	1238.0	1258.3	1278.6	1302.9	1328.6	1343.5	1357.0
15°	1143.3	1147.3	1158.2	1170.3	1181.2	1202.8	1228.5	1254.2	1275.9	1298.9	1311.0
17.5°	1081.0	1082.4	1110.8	1104.0	1139.2	1159.5	1173.0	1197.4	1232.6	1251.5	1270.5
20°	1020.2	1033.7	1045.9	1052.6	1071.6	1094.6	1133.8	1152.7	1181.2	1198.7	1215.0
22.5°	972.8	993.1	993.1	1009.3	1018.8	1040.4	1068.9	1105.4	1136.5	1148.7	1171.7
25°	930.9	940.3	956.6	962.0	979.6	998.5	1017.4	1056.7	1090.5	1106.7	1123.0
27.5°	876.7	888.9	910.6	910.6	933.6	953.9	976.9	1002.6	1036.4	1059.4	1077.0
30°	834.8	847.0	856.4	871.3	880.8	899.7	940.3	959.3	989.0	1009.3	1031.0
32.5°	795.6	805.0	813.1	829.4	840.2	861.9	883.5	917.3	943.0	962.0	985.0
35°	752.3	761.7	772.6	784.7	801.0	821.3	841.6	870.0	895.7	913.3	932.2
37.5°	711.7	718.4	734.7	742.8	756.3	775.3	801.0	830.7	853.7	867.3	886.2
40°	672.4	677.8	690.0	704.9	714.4	729.3	756.3	782.0	810.4	826.7	841.6
42.5°	630.5	637.3	648.1	663.0	677.8	694.1	709.0	738.7	764.4	778.0	794.2
45°	594.0	598.0	606.1	621.0	635.9	648.1	671.1	698.1	722.5	733.3	750.9
47.5°	550.7	554.7	566.9	573.7	589.9	606.1	629.1	656.2	677.8	688.7	704.9
50°	506.0	510.1	518.2	533.1	543.9	561.5	581.8	604.8	631.8	646.7	656.2
52.5°	462.7	470.8	477.6	489.8	503.3	520.9	539.8	561.5	584.5	599.4	610.2
55°	419.4	426.2	434.3	441.1	457.3	473.5	495.2	515.5	535.8	549.3	561.5
57.5°	370.7	380.2	388.3	401.8	414.0	427.5	451.9	468.1	492.5	502.0	512.8
60°	328.8	338.2	345.0	355.8	366.7	384.2	400.5	420.8	441.1	453.2	466.8
62.5°	293.6	297.7	301.7	312.5	323.4	339.6	355.8	376.1	397.8	404.5	415.4
65°	258.4	262.5	269.2	278.7	286.8	296.3	313.9	330.1	350.4	361.2	365.3
67.5°	228.7	232.7	234.1	240.8	247.6	258.4	267.9	284.1	303.1	309.8	318.0
70°	194.8	201.6	202.9	208.4	211.1	217.8	228.7	240.8	255.7	267.9	274.7
72.5°	155.6	165.1	167.8	175.9	179.9	186.7	194.8	204.3	213.8	219.2	224.6
75°	127.2	129.9	131.2	138.0	144.8	154.2	158.3	163.7	171.8	178.6	184.0
77.5°	105.5	106.9	108.2	108.2	109.6	115.0	123.1	129.9	135.3	138.0	142.1
80°	85.2	83.9	83.9	85.2	85.2	85.2	87.9	97.4	100.1	106.9	105.5
82.5°	66.3	63.6	64.9	63.6	63.6	63.6	63.6	64.9	64.9	69.0	71.7
85°	43.3	44.6	43.3	43.3	41.9	43.3	41.9	41.9	40.6	40.6	39.2
87.5°	23.0	24.4	23.0	23.0	21.6	23.0	21.6	21.6	20.3	20.3	17.6
90°	31.4	30.2	29.0	27.9	29.0	25.5	22.1	18.6	15.1	14.0	12.8
92.5°	77.8	89.4	115.0	161.4	216.0	239.2	178.8	117.3	80.1	69.6	59.2
95°	221.8	283.3	418.0	558.5	688.6	613.1	422.7	249.7	151.0	128.4	105.7
97.5°	571.3	724.6	960.3	1095.0	1059.0	790.8	470.3	269.4	171.9	146.9	121.9
100°	1139.1	1275.0	1369.0	1328.4	1099.6	743.2	437.8	265.9	184.6	162.0	139.3
102.5°	1459.6	1524.6	1504.9	1340.0	1024.2	673.5	409.9	270.6	199.7	179.4	159.1
105°	1647.7	1625.6	1509.5	1266.8	933.6	618.9	399.4	279.8	217.1	199.1	181.1
107.5°	1712.7	1622.2	1439.9	1162.3	853.5	579.4	397.1	294.9	239.2	222.4	205.5
110°	1690.7	1544.4	1330.7	1064.8	787.3	558.5	402.9	314.7	262.4	246.2	229.9

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1610.5	1442.2	1222.7	980.0	743.2	546.9	414.5	334.4	286.8	271.2	255.5
115°	1502.6	1331.9	1129.8	915.0	714.1	545.8	427.3	356.5	312.4	296.7	281.0
117.5°	1393.4	1236.6	1057.8	872.0	694.4	546.9	443.6	379.7	335.6	321.0	306.5
120°	1299.4	1160.0	1003.3	839.5	681.6	551.6	462.1	401.8	360.0	345.4	330.9
122.5°	1225.0	1098.5	960.3	812.8	673.5	559.7	479.6	425.0	384.3	368.6	353.0
125°	1161.2	1049.7	923.1	790.8	666.5	567.8	498.1	447.1	406.4	390.8	375.1
127.5°	1106.6	1004.4	889.5	769.9	663.0	577.1	513.2	466.8	427.3	411.6	396.0
130°	1056.7	962.6	858.1	753.6	659.5	586.4	528.3	484.2	445.9	430.2	414.5
132.5°	1009.1	923.1	829.1	738.5	658.4	593.4	542.3	499.3	462.1	447.0	432.0
135°	961.5	886.0	803.5	725.7	657.2	600.3	553.9	514.4	478.4	462.8	447.1
137.5°	916.2	848.8	779.1	714.1	654.9	605.0	563.2	524.9	490.0	475.5	461.0
140°	873.2	817.5	758.2	703.7	653.7	609.6	570.1	535.3	501.6	487.1	472.6
142.5°	833.7	787.3	738.5	694.4	651.4	613.1	577.1	543.4	510.9	497.6	484.2
145°	798.9	761.7	723.4	686.3	649.1	614.3	581.7	550.4	520.2	506.8	493.5
147.5°	773.3	742.0	710.6	678.1	645.6	614.3	585.2	556.2	528.3	516.7	505.1
150°	747.8	723.4	696.7	670.0	641.0	614.3	586.4	562.0	535.3	524.8	514.4
152.5°	726.9	706.0	683.9	660.7	635.2	610.8	588.7	565.5	543.4	533.6	523.7
155°	707.2	689.7	671.2	651.4	628.2	608.5	588.7	570.1	550.4	542.2	534.1
157.5°	687.4	673.5	657.2	641.0	622.4	605.0	589.9	572.5	556.2	549.8	543.4
160°	670.0	658.4	645.6	630.5	615.4	602.6	589.9	575.9	562.0	556.2	550.4
162.5°	652.6	642.1	631.7	620.1	608.5	598.0	588.7	577.1	565.5	560.8	556.2
165°	635.2	627.0	620.1	610.8	601.5	593.4	586.4	578.3	569.0	564.9	560.8
167.5°	620.1	615.4	609.6	601.5	594.5	588.7	585.2	578.3	571.3	568.4	565.5
170°	607.3	602.6	599.2	593.4	587.6	584.1	581.7	577.1	571.3	570.2	569.0
172.5°	595.7	592.2	589.9	585.2	581.7	580.6	580.6	577.1	572.5	571.9	571.3
175°	585.2	582.9	581.7	579.4	577.1	577.1	578.3	575.9	573.6	573.0	572.5
177.5°	578.3	577.1	575.9	574.8	573.6	574.8	577.1	574.8	573.6	573.6	573.6
180°	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6	573.6

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1580.3	1580.3	1580.3	1580.3
2.5°	1539.7	1549.2	1568.1	1584.3
5°	1507.2	1522.1	1550.5	1578.9
7.5°	1468.0	1491.0	1527.5	1566.8
10°	1430.1	1459.9	1504.5	1550.5
12.5°	1392.2	1423.3	1470.7	1530.2
15°	1347.6	1380.0	1436.9	1508.6
17.5°	1308.3	1351.6	1403.0	1474.8
20°	1266.4	1298.9	1365.2	1440.9
22.5°	1213.6	1267.7	1330.0	1409.8
25°	1171.7	1219.0	1281.3	1371.9
27.5°	1120.3	1175.7	1251.5	1331.3
30°	1078.3	1124.3	1194.7	1290.7
32.5°	1029.6	1083.7	1156.8	1251.5
35°	986.3	1032.3	1101.3	1197.4
37.5°	934.9	985.0	1062.1	1147.3
40°	890.3	939.0	1012.0	1091.9
42.5°	836.1	887.6	960.6	1028.3
45°	792.8	840.2	898.4	960.6
47.5°	740.1	790.1	847.0	890.3
50°	692.7	738.7	783.4	819.9
52.5°	641.3	683.3	723.8	750.9
55°	594.0	626.4	658.9	677.8
57.5°	538.5	569.6	596.7	607.5
60°	489.8	515.5	533.1	545.3
62.5°	438.4	457.3	470.8	477.6
65°	388.3	401.8	408.6	415.4
67.5°	336.9	349.1	353.1	361.2
70°	282.8	296.3	299.0	303.1
72.5°	242.2	242.2	247.6	253.0
75°	193.5	196.2	198.9	198.9
77.5°	151.5	151.5	154.2	155.6
80°	110.9	112.3	112.3	110.9
82.5°	75.8	78.5	75.8	74.4
85°	41.9	47.4	44.6	44.6
87.5°	17.6	17.6	20.3	17.6
90°	10.5	7.0	4.6	2.3
92.5°	47.6	37.2	25.5	17.4
95°	75.5	55.7	43.0	39.5
97.5°	91.7	74.3	63.9	62.7
100°	111.5	95.2	87.1	85.9
102.5°	134.7	119.6	112.6	110.3
105°	159.1	145.1	138.2	134.7
107.5°	184.6	170.7	163.7	160.2
110°	210.2	197.4	191.6	188.1

TEST NUMBER: P1012152

CATALOG NUMBER: S123RDIP-B1000D1195UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	235.7	222.9	217.1	213.7
115°	261.3	249.7	242.7	238.0
117.5°	284.5	274.0	268.2	262.4
120°	308.9	297.3	291.5	288.0
122.5°	332.1	319.3	313.5	310.0
125°	353.0	340.2	333.3	330.9
127.5°	371.6	358.8	350.7	347.2
130°	390.2	376.2	365.8	362.3
132.5°	407.6	390.2	378.5	373.9
135°	422.7	405.2	392.5	387.8
137.5°	436.6	418.0	405.2	400.6
140°	449.4	430.8	419.2	413.4
142.5°	461.0	444.7	432.0	427.3
145°	473.8	456.3	445.9	442.4
147.5°	485.4	470.3	459.8	457.5
150°	498.1	483.0	473.8	472.6
152.5°	509.8	497.0	487.7	487.7
155°	521.4	509.8	502.8	502.8
157.5°	531.8	521.4	515.6	514.4
160°	542.3	533.0	528.3	528.3
162.5°	549.2	542.3	538.8	538.8
165°	556.2	550.4	548.1	549.2
167.5°	562.0	557.4	556.2	557.4
170°	566.7	563.2	562.0	564.3
172.5°	570.1	567.8	567.8	569.0
175°	572.5	570.1	571.3	572.5
177.5°	573.6	572.5	573.6	574.8
180°	573.6	573.6	573.6	573.6

(END OF REPORT)