

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012274

Luminaire Tested: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012274
REPORT IS A COMBINATION OF REPORTS P992943 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8293.0 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	100	96	92	89	93	89	86	83	77	74	72	65	64	62	55	54	53
2	91	84	78	73	85	79	74	69	68	64	61	58	56	53	49	47	46
3	84	75	68	62	78	70	64	59	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	60	52	46	66	56	49	44	49	43	39	42	38	35	36	33	31
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27
7	61	49	41	35	56	46	39	34	40	35	31	35	31	27	30	27	24
8	56	44	37	32	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	29	25	30	25	22	26	23	20
10	49	37	30	26	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19894	19894	19894	19894
5°	19909	22912	19960	16998
10°	19732	27657	19819	14847
15°	19530	31390	19530	13091
20°	19129	33859	19237	11613
25°	18837	32168	18799	10596
30°	18495	22288	18457	9602
35°	18085	14310	18002	8853
40°	17573	10105	17487	8107
45°	16684	8086	16662	7381
50°	15593	6764	15541	6532
55°	14363	5575	14249	5537
60°	13159	4609	13026	4709
65°	11744	3688	11818	3991
70°	10437	2562	10716	3227
75°	8848	1900	9209	2481
80°	7047	1261	7644	1860
85°	5014	596	5475	1157

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 26558 cd/sqm

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.5	2.2
10°-20°	568.1	6.9
20°-30°	894.8	10.8
30°-40°	930.5	11.2
40°-50°	796.0	9.6
50°-60°	606.9	7.3
60°-70°	388.8	4.7
70°-80°	186.3	2.2
80°-90°	51.7	0.6
90°-100°	266.1	3.2
100°-110°	779.0	9.4
110°-120°	760.7	9.2
120°-130°	605.8	7.3
130°-140°	478.0	5.8
140°-150°	356.6	4.3
150°-160°	248.6	3.0
160°-170°	146.0	1.8
170°-180°	47.5	0.6
0°-30°	1644.5	19.8
0°-40°	2574.9	31.0
0°-60°	3977.9	48.0
0°-90°	4604.7	55.5
90°-120°	1805.8	21.8
90°-150°	3246.1	39.1
90°-180°	3688.0	44.5
0°-180°	8293.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1848	1848	1848	1848	1848	
5°	1847	2195	1851	1628	1847	175
15°	1764	3119	1764	1301	1764	496
25°	1604	3214	1601	1059	1604	739
35°	1400	1394	1394	862	1400	876
45°	1123	744	1122	679	1123	865
55°	793	467	786	464	793	710
65°	486	269	489	291	486	485
75°	233	114	242	149	233	251
85°	52	27	57	52	52	58
90°	2	29	2	29	2	5
95°	34	115	34	115	34	36
105°	115	1262	115	1262	115	122
115°	204	1536	204	1536	204	201
125°	283	1211	283	1211	283	251
135°	332	982	332	982	332	256
145°	378	767	378	767	378	237
155°	430	636	430	636	430	198
165°	470	555	470	555	470	132
175°	489	499	489	499	489	46
180°	490	490	490	490	490	

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1852.9	1865.6	1875.1	1881.4	1897.2	1906.7	1914.6	1928.9	1928.9	1932.0	1938.3
5°	1846.6	1873.5	1892.5	1917.8	1951.0	1966.8	1989.0	2008.0	2034.9	2049.1	2063.3
7.5°	1832.3	1870.3	1909.9	1947.8	1996.9	2028.5	2050.7	2099.7	2134.6	2177.3	2210.5
10°	1813.3	1865.6	1916.2	1974.7	2041.2	2088.7	2121.9	2186.8	2253.2	2313.4	2364.0
12.5°	1789.6	1852.9	1925.7	1996.9	2090.2	2137.7	2191.5	2272.2	2367.2	2443.1	2511.1
15°	1764.3	1837.1	1919.4	2006.4	2123.5	2189.9	2267.5	2365.6	2471.6	2580.8	2674.1
17.5°	1724.7	1816.5	1908.3	2034.9	2172.5	2212.1	2278.5	2413.0	2544.4	2642.5	2756.4
20°	1685.2	1788.0	1903.5	2017.5	2166.2	2258.0	2319.7	2462.1	2602.9	2721.6	2830.8
22.5°	1648.8	1756.4	1876.6	2020.6	2159.9	2251.6	2329.2	2477.9	2640.9	2773.8	2908.3
25°	1604.5	1721.6	1854.5	1990.6	2159.9	2229.5	2314.9	2487.4	2659.9	2813.4	2979.5
27.5°	1557.0	1675.7	1807.0	1946.3	2101.3	2204.2	2288.0	2473.2	2683.6	2848.2	3019.1
30°	1509.5	1631.4	1758.0	1883.0	2057.0	2155.1	2251.6	2455.8	2696.3	2884.6	3015.9
32.5°	1463.6	1566.5	1691.5	1813.3	1985.8	2093.4	2202.6	2438.4	2701.0	2859.3	2922.5
35°	1400.4	1508.0	1609.2	1739.0	1913.0	2019.0	2147.2	2436.8	2680.5	2778.6	2746.9
37.5°	1341.8	1432.0	1528.5	1644.0	1822.8	1960.5	2093.4	2395.6	2612.4	2618.7	2439.9
40°	1276.9	1351.3	1432.0	1553.8	1746.9	1883.0	2027.0	2332.3	2489.0	2395.6	2080.8
42.5°	1202.6	1269.0	1332.3	1451.0	1661.4	1813.3	1968.4	2253.2	2310.2	2095.0	1767.5
45°	1123.4	1177.2	1235.8	1360.8	1571.2	1721.6	1876.6	2131.4	2072.8	1769.0	1457.3
47.5°	1041.2	1087.1	1144.0	1257.9	1474.7	1628.2	1775.4	1957.3	1808.6	1482.6	1221.6
50°	958.9	995.3	1050.7	1167.8	1376.6	1515.9	1651.9	1770.6	1561.8	1272.2	1009.5
52.5°	878.2	906.7	963.6	1063.3	1265.9	1398.8	1496.9	1542.8	1330.7	1050.7	876.6
55°	792.7	824.4	862.4	963.6	1164.6	1262.7	1327.6	1326.0	1107.6	890.8	724.7
57.5°	710.5	738.9	772.2	873.4	1036.4	1102.9	1158.3	1131.4	924.1	729.5	621.9
60°	637.7	653.5	689.9	775.3	898.8	955.7	987.4	941.5	754.8	615.5	514.3
62.5°	558.6	574.4	604.4	685.1	761.1	791.2	818.1	759.5	623.4	501.6	439.9
65°	485.8	506.3	525.3	590.2	631.3	667.7	664.6	615.5	487.4	408.2	357.6
67.5°	422.5	430.4	446.2	485.8	504.8	531.7	533.2	477.9	392.4	332.3	302.2
70°	354.4	362.4	373.4	392.4	405.1	411.4	408.2	359.2	295.9	259.5	232.6
72.5°	295.9	294.3	302.2	302.2	314.9	313.3	303.8	265.8	224.7	194.6	178.8
75°	232.6	234.2	235.8	232.6	227.9	221.5	213.6	185.1	158.2	144.0	129.8
77.5°	182.0	178.8	180.4	169.3	163.0	156.6	145.6	131.3	109.2	106.0	99.7
80°	129.8	128.2	126.6	121.8	107.6	101.3	93.4	85.4	80.7	77.5	76.0
82.5°	87.0	87.0	83.9	74.4	66.5	61.7	60.1	57.0	52.2	52.2	50.6
85°	52.2	50.6	47.5	38.0	33.2	33.2	33.2	33.2	30.1	30.1	28.5
87.5°	20.6	19.0	14.2	14.2	12.7	12.7	12.7	11.1	11.1	9.5	9.5
90°	2.0	4.0	6.0	8.9	10.9	11.9	12.9	15.9	18.9	21.8	24.8
92.5°	14.9	21.8	31.8	40.7	50.6	59.6	68.5	100.2	152.9	204.5	184.6
95°	33.7	36.7	47.6	64.5	90.3	109.6	129.0	213.4	361.3	524.1	588.6
97.5°	53.6	54.6	63.5	78.4	104.2	125.6	146.9	230.3	402.0	675.9	905.2
100°	73.4	74.4	81.4	95.3	119.1	138.4	157.8	227.3	374.2	635.2	940.0
102.5°	94.3	96.3	102.2	115.1	136.0	153.4	170.7	231.3	350.4	575.7	875.4
105°	115.1	118.1	124.1	136.0	154.8	170.2	185.6	239.2	341.4	529.0	798.0
107.5°	137.0	140.0	145.9	157.8	175.7	190.1	204.5	252.1	339.5	495.3	729.5
110°	160.8	163.8	168.7	179.7	196.5	210.4	224.3	269.0	344.4	477.4	673.0

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	182.6	185.6	190.6	201.5	218.4	231.8	245.2	285.9	354.3	467.5	635.2
115°	203.5	207.4	213.4	223.3	240.2	253.6	267.0	304.7	365.3	466.5	610.4
117.5°	224.3	229.3	234.2	243.2	262.0	274.4	286.9	324.6	379.2	467.5	593.6
120°	246.2	249.1	254.1	264.0	282.9	295.3	307.7	343.4	395.0	471.5	582.6
122.5°	265.0	268.0	273.0	283.9	301.7	315.1	328.5	363.3	409.9	478.4	575.7
125°	282.9	284.9	290.8	301.7	320.6	334.0	347.4	382.1	425.8	485.4	569.7
127.5°	296.8	299.8	306.7	317.6	338.5	351.9	365.3	399.0	438.7	493.3	566.8
130°	309.7	312.7	321.6	333.5	354.3	367.7	381.1	413.9	451.6	501.2	563.8
132.5°	319.6	323.6	333.5	348.4	369.2	382.1	395.0	426.8	463.5	507.2	562.8
135°	331.5	335.5	346.4	361.3	382.1	395.5	408.9	439.7	473.5	513.2	561.8
137.5°	342.4	346.4	357.3	373.2	394.0	406.4	418.9	448.6	481.4	517.1	559.8
140°	353.4	358.3	368.2	384.1	404.0	416.4	428.8	457.6	487.3	521.1	558.8
142.5°	365.3	369.2	380.2	394.0	413.9	425.3	436.7	464.5	493.3	524.1	556.8
145°	378.2	381.1	390.1	405.0	421.8	433.2	444.7	470.5	497.3	525.1	554.8
147.5°	391.1	393.1	402.0	414.9	431.8	441.7	451.6	475.4	500.3	525.1	551.9
150°	404.0	405.0	412.9	425.8	439.7	448.6	457.6	480.4	501.2	525.1	547.9
152.5°	416.9	416.9	424.8	435.7	447.6	456.0	464.5	483.4	503.2	522.1	542.9
155°	429.8	429.8	435.7	445.7	456.6	463.6	470.5	487.3	503.2	520.1	537.0
157.5°	439.7	440.7	445.7	454.6	464.5	470.0	475.4	489.3	504.2	517.1	532.0
160°	451.6	451.6	455.6	463.5	470.5	475.4	480.4	492.3	504.2	515.1	526.1
162.5°	460.5	460.5	463.5	469.5	475.4	479.4	483.4	493.3	503.2	511.2	520.1
165°	469.5	468.5	470.5	475.4	479.4	482.9	486.4	494.3	501.2	507.2	514.1
167.5°	476.4	475.4	476.4	480.4	483.4	485.8	488.3	494.3	500.3	503.2	508.2
170°	482.4	480.4	481.4	484.4	486.4	487.4	488.3	493.3	497.3	499.3	502.2
172.5°	486.4	485.4	485.4	487.3	488.3	488.8	489.3	493.3	496.3	496.3	497.3
175°	489.3	488.3	487.3	489.3	489.3	489.8	490.3	492.3	494.3	493.3	493.3
177.5°	491.3	490.3	489.3	490.3	490.3	490.3	490.3	491.3	493.3	491.3	490.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1951.0	1951.0	1965.2	1979.5	1971.6	1976.3	1993.7	1987.4	2000.1	1998.5	2003.2
5°	2098.2	2115.6	2129.8	2159.9	2164.6	2159.9	2189.9	2197.8	2212.1	2194.7	2202.6
7.5°	2264.3	2300.7	2335.5	2379.8	2394.1	2397.2	2413.0	2435.2	2454.2	2419.4	2436.8
10°	2425.7	2481.1	2552.3	2591.8	2626.7	2639.3	2652.0	2666.2	2688.4	2708.9	2693.1
12.5°	2599.8	2680.5	2748.5	2819.7	2862.4	2857.7	2894.1	2903.6	2921.0	2925.7	2932.0
15°	2742.2	2856.1	2898.8	3004.8	3014.3	3046.0	3087.1	3123.5	3128.3	3118.8	3118.8
17.5°	2878.2	2976.3	3052.3	3137.7	3155.1	3182.0	3234.3	3251.7	3258.0	3256.4	3256.4
20°	2989.0	3053.9	3182.0	3253.3	3281.7	3316.5	3352.9	3375.1	3379.8	3386.2	3376.7
22.5°	3061.8	3159.9	3264.3	3322.9	3346.6	3359.3	3383.0	3389.3	3381.4	3383.0	3384.6
25°	3118.8	3215.3	3278.6	3294.4	3292.8	3277.0	3259.6	3229.5	3226.4	3213.7	3188.4
27.5°	3134.6	3171.0	3163.1	3098.2	3033.3	3027.0	2922.5	2865.6	2800.7	2810.2	2773.8
30°	3049.1	3001.7	2889.3	2724.8	2656.7	2546.0	2428.9	2307.0	2259.6	2207.3	2303.9
32.5°	2840.3	2671.0	2471.6	2258.0	2144.0	2045.9	1920.9	1832.3	1781.7	1739.0	1821.3
35°	2525.4	2261.1	1996.9	1794.4	1701.0	1612.4	1495.3	1451.0	1387.7	1394.0	1401.9
37.5°	2120.3	1829.2	1629.8	1430.4	1368.7	1332.3	1246.9	1178.8	1156.7	1150.3	1150.3
40°	1740.6	1501.6	1324.4	1167.8	1120.3	1090.2	1022.2	990.5	966.8	960.5	968.4
42.5°	1439.9	1235.8	1098.1	993.7	960.5	922.5	894.0	854.5	849.7	838.6	852.9
45°	1208.9	1031.7	928.8	852.9	824.4	810.1	778.5	754.8	745.3	743.7	754.8
47.5°	1025.3	887.7	797.5	750.0	727.9	713.6	686.7	677.2	667.7	670.9	666.2
50°	860.8	757.9	699.4	656.7	642.4	628.2	610.8	601.3	596.5	596.5	595.0
52.5°	738.9	653.5	615.5	576.0	569.6	561.7	542.7	536.4	528.5	526.9	533.2
55°	632.9	574.4	536.4	512.7	506.3	490.5	482.6	474.7	469.9	466.8	468.4
57.5°	541.2	496.8	471.5	451.0	439.9	433.6	419.3	417.7	414.6	414.6	413.0
60°	465.2	433.6	403.5	390.8	382.9	375.0	373.4	363.9	359.2	362.4	360.8
62.5°	394.0	368.7	351.3	337.0	332.3	326.0	321.2	318.0	313.3	314.9	314.9
65°	329.1	308.6	295.9	283.2	281.7	275.3	273.7	270.6	270.6	269.0	272.2
67.5°	270.6	256.3	245.3	237.3	232.6	234.2	227.9	223.1	223.1	221.5	226.3
70°	215.2	207.3	196.2	186.7	180.4	180.4	172.5	170.9	170.9	170.9	169.3
72.5°	166.1	151.9	147.2	144.0	144.0	144.0	140.8	140.8	139.2	140.8	139.2
75°	123.4	121.8	118.7	117.1	117.1	115.5	113.9	113.9	113.9	113.9	113.9
77.5°	96.5	96.5	93.4	91.8	91.8	91.8	90.2	90.2	88.6	88.6	88.6
80°	71.2	71.2	68.0	68.0	68.0	66.5	66.5	66.5	68.0	66.5	66.5
82.5°	49.1	49.1	47.5	49.1	47.5	45.9	45.9	45.9	44.3	45.9	45.9
85°	28.5	28.5	26.9	25.3	26.9	26.9	25.3	26.9	25.3	26.9	25.3
87.5°	11.1	9.5	9.5	9.5	7.9	9.5	7.9	7.9	9.5	7.9	9.5
90°	23.8	24.8	25.8	26.8	27.8	28.8	27.8	28.8	29.8	28.8	29.8
92.5°	138.0	98.3	76.4	66.5	63.0	59.6	57.6	53.6	54.6	52.6	54.6
95°	477.4	357.3	242.2	189.6	171.7	153.8	135.0	126.1	119.1	115.1	119.1
97.5°	936.0	820.9	619.4	488.3	431.8	375.2	308.7	271.0	247.1	236.2	247.1
100°	1135.5	1170.2	1089.8	973.7	903.2	832.8	732.5	660.1	621.3	622.3	621.3
102.5°	1145.4	1286.4	1303.2	1247.7	1209.4	1171.2	1098.8	1045.2	1014.4	985.6	1014.4
105°	1082.9	1290.3	1389.6	1408.4	1395.5	1382.6	1337.0	1299.3	1267.5	1262.5	1267.5
107.5°	993.6	1230.8	1386.6	1464.0	1477.4	1490.8	1484.9	1467.0	1454.1	1443.2	1454.1
110°	910.2	1137.5	1320.1	1445.2	1480.0	1514.7	1542.4	1550.4	1548.4	1546.4	1548.4

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	837.7	1045.2	1232.8	1376.7	1423.8	1471.0	1527.6	1556.3	1566.3	1567.3	1566.3
115°	782.1	965.8	1138.5	1284.4	1338.5	1392.6	1467.0	1510.7	1530.5	1535.5	1530.5
117.5°	745.4	904.2	1057.1	1191.1	1247.2	1303.2	1380.7	1429.3	1459.1	1466.0	1459.1
120°	717.6	857.6	991.6	1110.7	1160.8	1210.9	1289.3	1344.9	1368.7	1374.7	1368.7
122.5°	694.8	820.9	939.0	1047.2	1092.8	1138.5	1206.0	1254.6	1281.4	1289.3	1281.4
125°	675.9	789.1	897.3	992.6	1032.3	1072.0	1135.5	1179.2	1204.0	1210.9	1204.0
127.5°	658.1	760.3	858.6	945.9	982.6	1019.4	1076.9	1114.6	1137.5	1143.4	1137.5
130°	644.2	733.5	822.8	903.2	937.0	970.7	1023.3	1059.1	1079.9	1087.8	1079.9
132.5°	631.3	708.7	789.1	862.5	894.3	926.1	974.7	1010.4	1028.3	1033.3	1028.3
135°	620.4	686.9	757.3	821.8	850.1	878.4	927.1	956.8	974.7	981.6	974.7
137.5°	610.4	666.0	725.6	783.1	808.4	833.8	875.4	906.2	921.1	927.1	921.1
140°	601.5	648.1	698.8	746.4	767.8	789.1	826.8	854.6	870.5	869.5	870.5
142.5°	593.6	631.3	673.0	712.7	730.6	748.4	779.2	803.0	816.9	815.9	816.9
145°	586.6	618.4	651.1	682.9	697.3	711.7	736.5	757.3	765.3	767.3	765.3
147.5°	579.7	607.4	634.2	661.0	671.4	681.9	701.7	716.6	724.6	725.6	724.6
150°	572.7	595.5	618.4	639.2	648.7	658.1	673.0	683.9	689.8	689.8	689.8
152.5°	564.8	584.6	603.5	621.3	628.8	636.2	647.2	657.1	660.1	660.1	660.1
155°	556.8	573.7	589.6	604.5	610.4	616.4	625.3	633.3	635.2	636.2	635.2
157.5°	547.9	561.8	575.7	587.6	592.6	597.5	605.5	611.4	613.4	613.4	613.4
160°	539.0	551.9	562.8	572.7	576.2	579.7	586.6	592.6	592.6	591.6	592.6
162.5°	530.0	540.0	548.9	557.8	560.8	563.8	567.7	572.7	572.7	571.7	572.7
165°	522.1	530.0	536.0	542.9	545.4	547.9	551.9	555.8	554.8	554.8	554.8
167.5°	514.1	521.1	526.1	530.0	532.0	534.0	536.0	539.0	538.0	538.0	538.0
170°	507.2	512.2	515.1	519.1	520.1	521.1	522.1	524.1	523.1	523.1	523.1
172.5°	500.3	504.2	506.2	509.2	509.7	510.2	510.2	512.2	510.2	509.2	510.2
175°	495.3	497.3	498.3	500.3	500.3	500.3	500.3	501.2	500.3	499.3	500.3
177.5°	491.3	492.3	493.3	494.3	494.3	494.3	493.3	494.3	492.3	492.3	492.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1995.3	1985.8	1979.5	1974.7	1970.0	1984.2	1965.2	1944.7	1930.4	1920.9	1917.8
5°	2204.2	2183.6	2166.2	2152.0	2155.1	2155.1	2121.9	2085.5	2053.9	2036.4	2017.5
7.5°	2446.3	2424.1	2389.3	2381.4	2375.1	2335.5	2302.3	2235.8	2196.3	2156.7	2121.9
10°	2686.8	2658.3	2625.1	2614.0	2598.2	2549.1	2498.5	2413.0	2364.0	2291.2	2245.3
12.5°	2911.5	2876.7	2843.4	2835.5	2811.8	2769.1	2682.0	2593.4	2509.6	2432.0	2351.3
15°	3099.8	3090.3	3039.6	3008.0	2955.8	2897.2	2878.2	2758.0	2652.0	2571.3	2425.7
17.5°	3258.0	3213.7	3166.2	3145.7	3125.1	3057.0	2989.0	2865.6	2751.7	2633.0	2539.6
20°	3384.6	3335.5	3302.3	3272.2	3262.7	3185.2	3077.6	2968.4	2843.4	2710.5	2588.7
22.5°	3390.9	3384.6	3362.4	3345.0	3326.0	3275.4	3190.0	3053.9	2921.0	2775.4	2615.6
25°	3259.6	3250.1	3313.4	3297.6	3310.2	3291.2	3245.3	3131.4	2976.3	2805.5	2644.1
27.5°	2864.0	2960.5	3060.2	3095.0	3118.8	3186.8	3208.9	3145.7	3020.7	2838.7	2658.3
30°	2326.0	2454.2	2615.6	2702.6	2769.1	2895.6	3060.2	3080.8	3022.2	2876.7	2655.1
32.5°	1826.0	1943.1	2072.8	2175.7	2264.3	2523.8	2745.3	2905.1	2933.6	2857.7	2663.0
35°	1471.6	1522.2	1645.6	1743.7	1864.0	2085.5	2346.6	2604.5	2778.6	2788.1	2639.3
37.5°	1213.6	1240.5	1348.1	1403.5	1474.7	1669.3	1913.0	2250.1	2520.6	2648.8	2572.9
40°	1004.8	1066.5	1128.2	1159.8	1210.5	1345.0	1579.2	1843.4	2178.9	2416.2	2470.0
42.5°	871.9	898.8	938.3	982.6	1014.3	1131.4	1288.0	1530.1	1832.3	2163.0	2311.8
45°	769.0	778.5	819.6	848.1	881.4	963.6	1074.4	1276.9	1542.8	1868.7	2121.9
47.5°	683.6	702.6	724.7	742.1	764.3	827.6	922.5	1069.6	1303.8	1595.0	1867.1
50°	607.6	618.7	647.2	655.1	670.9	715.2	788.0	900.3	1093.4	1326.0	1607.6
52.5°	536.4	557.0	568.1	579.1	593.4	629.8	677.2	769.0	914.6	1132.9	1371.9
55°	481.0	487.4	503.2	512.7	523.7	549.1	590.2	658.2	772.2	946.2	1172.5
57.5°	427.2	427.2	443.1	451.0	462.0	481.0	517.4	569.6	651.9	781.7	989.0
60°	370.3	371.8	384.5	394.0	397.2	416.2	446.2	487.4	550.6	645.6	814.9
62.5°	319.6	327.5	333.9	337.0	348.1	359.2	384.5	413.0	457.3	541.2	661.4
65°	276.9	278.5	283.2	286.4	291.1	303.8	322.8	341.8	379.8	441.5	539.6
67.5°	227.9	234.2	240.5	240.5	245.3	251.6	270.6	286.4	314.9	351.3	417.7
70°	170.9	174.1	183.5	188.3	194.6	205.7	215.2	224.7	246.8	273.7	324.4
72.5°	142.4	142.4	145.6	147.2	147.2	155.1	169.3	178.8	189.9	208.9	243.7
75°	113.9	113.9	118.7	117.1	120.3	123.4	125.0	131.3	137.7	151.9	172.5
77.5°	90.2	91.8	91.8	93.4	93.4	94.9	96.5	99.7	102.9	110.8	120.3
80°	66.5	68.0	68.0	69.6	69.6	71.2	72.8	74.4	77.5	80.7	85.4
82.5°	45.9	47.5	47.5	49.1	47.5	49.1	50.6	50.6	52.2	55.4	57.0
85°	26.9	26.9	28.5	26.9	26.9	26.9	28.5	28.5	30.1	34.8	34.8
87.5°	7.9	9.5	7.9	9.5	9.5	9.5	9.5	11.1	11.1	12.7	14.2
90°	28.8	27.8	28.8	27.8	26.8	25.8	24.8	23.8	24.8	21.8	18.9
92.5°	53.6	57.6	59.6	63.0	66.5	76.4	98.3	138.0	184.6	204.5	152.9
95°	126.1	135.0	153.8	171.7	189.6	242.2	357.3	477.4	588.6	524.1	361.3
97.5°	271.0	308.7	375.2	431.8	488.3	619.4	820.9	936.0	905.2	675.9	402.0
100°	660.1	732.5	832.8	903.2	973.7	1089.8	1170.2	1135.5	940.0	635.2	374.2
102.5°	1045.2	1098.8	1171.2	1209.4	1247.7	1303.2	1286.4	1145.4	875.4	575.7	350.4
105°	1299.3	1337.0	1382.6	1395.5	1408.4	1389.6	1290.3	1082.9	798.0	529.0	341.4
107.5°	1467.0	1484.9	1490.8	1477.4	1464.0	1386.6	1230.8	993.6	729.5	495.3	339.5
110°	1550.4	1542.4	1514.7	1480.0	1445.2	1320.1	1137.5	910.2	673.0	477.4	344.4

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1556.3	1527.6	1471.0	1423.8	1376.7	1232.8	1045.2	837.7	635.2	467.5	354.3
115°	1510.7	1467.0	1392.6	1338.5	1284.4	1138.5	965.8	782.1	610.4	466.5	365.3
117.5°	1429.3	1380.7	1303.2	1247.2	1191.1	1057.1	904.2	745.4	593.6	467.5	379.2
120°	1344.9	1289.3	1210.9	1160.8	1110.7	991.6	857.6	717.6	582.6	471.5	395.0
122.5°	1254.6	1206.0	1138.5	1092.8	1047.2	939.0	820.9	694.8	575.7	478.4	409.9
125°	1179.2	1135.5	1072.0	1032.3	992.6	897.3	789.1	675.9	569.7	485.4	425.8
127.5°	1114.6	1076.9	1019.4	982.6	945.9	858.6	760.3	658.1	566.8	493.3	438.7
130°	1059.1	1023.3	970.7	937.0	903.2	822.8	733.5	644.2	563.8	501.2	451.6
132.5°	1010.4	974.7	926.1	894.3	862.5	789.1	708.7	631.3	562.8	507.2	463.5
135°	956.8	927.1	878.4	850.1	821.8	757.3	686.9	620.4	561.8	513.2	473.5
137.5°	906.2	875.4	833.8	808.4	783.1	725.6	666.0	610.4	559.8	517.1	481.4
140°	854.6	826.8	789.1	767.8	746.4	698.8	648.1	601.5	558.8	521.1	487.3
142.5°	803.0	779.2	748.4	730.6	712.7	673.0	631.3	593.6	556.8	524.1	493.3
145°	757.3	736.5	711.7	697.3	682.9	651.1	618.4	586.6	554.8	525.1	497.3
147.5°	716.6	701.7	681.9	671.4	661.0	634.2	607.4	579.7	551.9	525.1	500.3
150°	683.9	673.0	658.1	648.7	639.2	618.4	595.5	572.7	547.9	525.1	501.2
152.5°	657.1	647.2	636.2	628.8	621.3	603.5	584.6	564.8	542.9	522.1	503.2
155°	633.3	625.3	616.4	610.4	604.5	589.6	573.7	556.8	537.0	520.1	503.2
157.5°	611.4	605.5	597.5	592.6	587.6	575.7	561.8	547.9	532.0	517.1	504.2
160°	592.6	586.6	579.7	576.2	572.7	562.8	551.9	539.0	526.1	515.1	504.2
162.5°	572.7	567.7	563.8	560.8	557.8	548.9	540.0	530.0	520.1	511.2	503.2
165°	555.8	551.9	547.9	545.4	542.9	536.0	530.0	522.1	514.1	507.2	501.2
167.5°	539.0	536.0	534.0	532.0	530.0	526.1	521.1	514.1	508.2	503.2	500.3
170°	524.1	522.1	521.1	520.1	519.1	515.1	512.2	507.2	502.2	499.3	497.3
172.5°	512.2	510.2	510.2	509.7	509.2	506.2	504.2	500.3	497.3	496.3	496.3
175°	501.2	500.3	500.3	500.3	500.3	498.3	497.3	495.3	493.3	493.3	494.3
177.5°	494.3	493.3	494.3	494.3	494.3	493.3	492.3	491.3	490.3	491.3	493.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1913.0	1905.1	1897.2	1897.2	1879.8	1864.0	1856.1	1859.2	1849.7	1837.1	1824.4
5°	1996.9	1965.2	1958.9	1941.5	1917.8	1884.5	1867.1	1851.3	1832.3	1807.0	1783.3
7.5°	2074.4	2033.3	2011.1	1993.7	1947.8	1902.0	1864.0	1838.7	1805.4	1767.5	1739.0
10°	2175.7	2099.7	2076.0	2036.4	1971.6	1906.7	1862.4	1821.3	1775.4	1731.1	1693.1
12.5°	2256.4	2169.4	2125.1	2085.5	2001.6	1919.4	1845.0	1794.4	1739.0	1689.9	1640.9
15°	2348.2	2250.1	2172.5	2125.1	2019.0	1919.4	1835.5	1764.3	1702.6	1642.4	1599.7
17.5°	2392.5	2269.0	2234.2	2166.2	2012.7	1913.0	1810.2	1734.2	1659.9	1590.2	1539.6
20°	2462.1	2318.1	2231.1	2185.2	2049.1	1902.0	1781.7	1694.7	1617.1	1542.8	1489.0
22.5°	2466.8	2310.2	2253.2	2166.2	1998.5	1868.7	1756.4	1650.4	1560.2	1490.5	1435.2
25°	2455.8	2295.9	2216.8	2147.2	2008.0	1849.7	1705.7	1601.3	1512.7	1432.0	1367.1
27.5°	2451.0	2254.8	2180.4	2110.8	1954.2	1794.4	1675.7	1557.0	1455.7	1384.5	1318.1
30°	2444.7	2210.5	2120.3	2039.6	1895.6	1751.6	1609.2	1506.4	1409.8	1319.7	1253.2
32.5°	2403.5	2150.4	2058.6	1973.2	1818.1	1674.1	1561.8	1452.6	1348.1	1264.3	1204.1
35°	2390.9	2095.0	1974.7	1883.0	1731.1	1602.9	1484.2	1394.0	1295.9	1212.1	1140.9
37.5°	2354.5	2038.0	1908.3	1791.2	1633.0	1511.1	1424.1	1333.9	1239.0	1148.8	1091.8
40°	2291.2	1971.6	1824.4	1704.2	1541.2	1417.8	1337.1	1270.6	1177.2	1096.5	1026.9
42.5°	2197.8	1903.5	1745.3	1618.7	1438.3	1322.8	1256.4	1193.1	1114.0	1030.1	973.1
45°	2090.2	1813.3	1666.2	1525.4	1341.8	1229.5	1159.8	1121.9	1049.1	977.9	911.4
47.5°	1943.1	1720.0	1574.4	1428.8	1242.1	1132.9	1077.6	1039.6	989.0	911.4	857.6
50°	1758.0	1599.7	1462.1	1332.3	1144.0	1039.6	984.2	955.7	913.0	857.6	805.4
52.5°	1552.3	1460.5	1346.6	1226.3	1044.3	946.2	895.6	873.4	841.8	789.6	745.3
55°	1345.0	1305.4	1227.9	1109.2	939.9	859.2	814.9	786.4	762.7	724.7	686.7
57.5°	1159.8	1140.9	1087.1	995.3	852.9	769.0	731.0	712.0	693.1	664.6	626.6
60°	968.4	989.0	933.6	887.7	757.9	685.1	651.9	631.3	621.9	596.5	572.8
62.5°	802.2	821.2	789.6	754.8	663.0	598.1	577.5	558.6	552.2	530.1	506.3
65°	651.9	675.7	651.9	632.9	577.5	523.7	498.4	488.9	482.6	468.4	449.4
67.5°	519.0	542.7	531.7	507.9	490.5	446.2	432.0	422.5	419.3	408.2	392.4
70°	390.8	424.1	427.2	413.0	397.2	376.6	367.1	363.9	356.0	346.5	337.0
72.5°	281.7	319.6	321.2	321.2	311.7	311.7	302.2	297.5	297.5	288.0	276.9
75°	207.3	232.6	235.8	238.9	243.7	248.4	242.1	242.1	240.5	231.0	226.3
77.5°	137.7	159.8	167.7	178.8	185.1	185.1	188.3	191.5	188.3	183.5	180.4
80°	88.6	104.4	113.9	120.3	129.8	134.5	139.2	140.8	137.7	136.1	131.3
82.5°	58.5	63.3	68.0	76.0	87.0	94.9	94.9	93.4	96.5	94.9	93.4
85°	33.2	36.4	38.0	39.6	45.9	53.8	55.4	57.0	60.1	57.0	53.8
87.5°	12.7	14.2	14.2	14.2	17.4	19.0	23.7	30.1	28.5	25.3	25.3
90°	15.9	12.9	11.9	10.9	8.9	6.0	4.0	2.0	4.0	6.0	8.9
92.5°	100.2	68.5	59.6	50.6	40.7	31.8	21.8	14.9	21.8	31.8	40.7
95°	213.4	129.0	109.6	90.3	64.5	47.6	36.7	33.7	36.7	47.6	64.5
97.5°	230.3	146.9	125.6	104.2	78.4	63.5	54.6	53.6	54.6	63.5	78.4
100°	227.3	157.8	138.4	119.1	95.3	81.4	74.4	73.4	74.4	81.4	95.3
102.5°	231.3	170.7	153.4	136.0	115.1	102.2	96.3	94.3	96.3	102.2	115.1
105°	239.2	185.6	170.2	154.8	136.0	124.1	118.1	115.1	118.1	124.1	136.0
107.5°	252.1	204.5	190.1	175.7	157.8	145.9	140.0	137.0	140.0	145.9	157.8
110°	269.0	224.3	210.4	196.5	179.7	168.7	163.8	160.8	163.8	168.7	179.7



TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	285.9	245.2	231.8	218.4	201.5	190.6	185.6	182.6	185.6	190.6	201.5
115°	304.7	267.0	253.6	240.2	223.3	213.4	207.4	203.5	207.4	213.4	223.3
117.5°	324.6	286.9	274.4	262.0	243.2	234.2	229.3	224.3	229.3	234.2	243.2
120°	343.4	307.7	295.3	282.9	264.0	254.1	249.1	246.2	249.1	254.1	264.0
122.5°	363.3	328.5	315.1	301.7	283.9	273.0	268.0	265.0	268.0	273.0	283.9
125°	382.1	347.4	334.0	320.6	301.7	290.8	284.9	282.9	284.9	290.8	301.7
127.5°	399.0	365.3	351.9	338.5	317.6	306.7	299.8	296.8	299.8	306.7	317.6
130°	413.9	381.1	367.7	354.3	333.5	321.6	312.7	309.7	312.7	321.6	333.5
132.5°	426.8	395.0	382.1	369.2	348.4	333.5	323.6	319.6	323.6	333.5	348.4
135°	439.7	408.9	395.5	382.1	361.3	346.4	335.5	331.5	335.5	346.4	361.3
137.5°	448.6	418.9	406.4	394.0	373.2	357.3	346.4	342.4	346.4	357.3	373.2
140°	457.6	428.8	416.4	404.0	384.1	368.2	358.3	353.4	358.3	368.2	384.1
142.5°	464.5	436.7	425.3	413.9	394.0	380.2	369.2	365.3	369.2	380.2	394.0
145°	470.5	444.7	433.2	421.8	405.0	390.1	381.1	378.2	381.1	390.1	405.0
147.5°	475.4	451.6	441.7	431.8	414.9	402.0	393.1	391.1	393.1	402.0	414.9
150°	480.4	457.6	448.6	439.7	425.8	412.9	405.0	404.0	405.0	412.9	425.8
152.5°	483.4	464.5	456.0	447.6	435.7	424.8	416.9	416.9	416.9	424.8	435.7
155°	487.3	470.5	463.6	456.6	445.7	435.7	429.8	429.8	429.8	435.7	445.7
157.5°	489.3	475.4	470.0	464.5	454.6	445.7	440.7	439.7	440.7	445.7	454.6
160°	492.3	480.4	475.4	470.5	463.5	455.6	451.6	451.6	451.6	455.6	463.5
162.5°	493.3	483.4	479.4	475.4	469.5	463.5	460.5	460.5	460.5	463.5	469.5
165°	494.3	486.4	482.9	479.4	475.4	470.5	468.5	469.5	468.5	470.5	475.4
167.5°	494.3	488.3	485.8	483.4	480.4	476.4	475.4	476.4	475.4	476.4	480.4
170°	493.3	488.3	487.4	486.4	484.4	481.4	480.4	482.4	480.4	481.4	484.4
172.5°	493.3	489.3	488.8	488.3	487.3	485.4	485.4	486.4	485.4	485.4	487.3
175°	492.3	490.3	489.8	489.3	489.3	487.3	488.3	489.3	488.3	487.3	489.3
177.5°	491.3	490.3	490.3	490.3	490.3	489.3	490.3	491.3	490.3	489.3	490.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1824.4	1816.5	1813.3	1805.4	1786.4	1773.8	1759.5	1750.0	1751.6	1743.7	1748.5
5°	1767.5	1765.9	1754.8	1739.0	1712.1	1697.8	1672.5	1659.9	1653.5	1655.1	1645.6
7.5°	1720.0	1705.7	1697.8	1672.5	1647.2	1617.1	1596.6	1585.5	1576.0	1566.5	1560.2
10°	1666.2	1653.5	1640.9	1614.0	1579.2	1550.7	1522.2	1511.1	1496.9	1490.5	1485.8
12.5°	1609.2	1601.3	1585.5	1553.8	1514.3	1487.4	1454.2	1447.8	1428.8	1416.2	1413.0
15°	1557.0	1552.3	1523.8	1487.4	1447.8	1420.9	1392.4	1373.5	1341.8	1348.1	1337.1
17.5°	1501.6	1481.1	1463.6	1414.6	1395.6	1354.5	1321.2	1311.7	1289.6	1275.4	1261.1
20°	1439.9	1427.3	1405.1	1373.5	1327.6	1280.1	1254.8	1239.0	1226.3	1204.1	1197.8
22.5°	1381.4	1365.5	1346.6	1305.4	1265.9	1226.3	1191.5	1177.2	1161.4	1145.6	1136.1
25°	1335.5	1311.7	1291.2	1240.5	1201.0	1167.8	1145.6	1121.9	1099.7	1090.2	1087.1
27.5°	1264.3	1250.0	1229.5	1182.0	1145.6	1109.2	1088.6	1072.8	1049.1	1038.0	1028.5
30°	1218.4	1189.9	1166.2	1128.2	1091.8	1052.2	1033.3	1014.3	1000.0	985.8	974.7
32.5°	1156.7	1134.5	1115.5	1077.6	1041.2	1004.8	984.2	955.7	947.8	936.7	924.1
35°	1096.5	1082.3	1061.7	1020.6	981.0	955.7	933.6	906.7	897.2	889.3	878.2
37.5°	1039.6	1019.0	1004.8	965.2	930.4	900.3	882.9	860.8	854.5	845.0	837.0
40°	990.5	970.0	955.7	916.2	879.8	848.1	837.0	814.9	805.4	794.3	789.6
42.5°	935.2	917.7	898.8	870.3	832.3	800.7	778.5	765.8	753.2	748.4	738.9
45°	876.6	860.8	846.5	814.9	775.3	753.2	734.2	716.8	707.3	699.4	693.1
47.5°	826.0	811.7	792.7	757.9	726.3	705.7	686.7	669.3	659.8	650.3	642.4
50°	767.4	759.5	738.9	705.7	675.7	651.9	634.5	618.7	612.4	601.3	588.6
52.5°	715.2	701.0	683.6	656.7	629.8	601.3	577.5	568.1	557.0	550.6	539.6
55°	653.5	644.0	625.0	601.3	572.8	549.1	531.7	519.0	504.8	498.4	484.2
57.5°	601.3	583.9	574.4	544.3	517.4	493.7	481.0	468.4	452.5	443.1	436.7
60°	544.3	528.5	514.3	488.9	469.9	444.6	425.6	414.6	403.5	390.8	384.5
62.5°	488.9	476.3	458.9	438.3	414.6	394.0	379.8	363.9	357.6	344.9	340.2
65°	428.8	419.3	405.1	381.3	362.4	344.9	330.7	318.0	311.7	307.0	303.8
67.5°	375.0	362.4	352.9	332.3	311.7	297.5	289.6	281.7	273.7	269.0	264.2
70°	319.6	310.1	300.6	281.7	267.4	254.8	248.4	242.1	237.3	232.6	227.9
72.5°	262.7	257.9	248.4	235.8	224.7	215.2	210.4	202.5	197.8	189.9	186.7
75°	216.8	208.9	204.1	193.0	183.5	175.6	169.3	159.8	153.5	150.3	148.7
77.5°	170.9	167.7	161.4	151.9	147.2	139.2	129.8	126.6	123.4	123.4	121.8
80°	128.2	123.4	118.7	110.8	106.0	99.7	99.7	99.7	98.1	99.7	98.1
82.5°	87.0	83.9	80.7	76.0	74.4	74.4	76.0	76.0	76.0	76.0	76.0
85°	50.6	50.6	50.6	52.2	50.6	50.6	52.2	53.8	52.2	52.2	50.6
87.5°	23.7	23.7	25.3	25.3	26.9	26.9	26.9	26.9	26.9	26.9	28.5
90°	10.9	11.9	12.9	15.9	18.9	21.8	24.8	23.8	24.8	25.8	26.8
92.5°	50.6	59.6	68.5	100.2	152.9	204.5	184.6	138.0	98.3	76.4	66.5
95°	90.3	109.6	129.0	213.4	361.3	524.1	588.6	477.4	357.3	242.2	189.6
97.5°	104.2	125.6	146.9	230.3	402.0	675.9	905.2	936.0	820.9	619.4	488.3
100°	119.1	138.4	157.8	227.3	374.2	635.2	940.0	1135.5	1170.2	1089.8	973.7
102.5°	136.0	153.4	170.7	231.3	350.4	575.7	875.4	1145.4	1286.4	1303.2	1247.7
105°	154.8	170.2	185.6	239.2	341.4	529.0	798.0	1082.9	1290.3	1389.6	1408.4
107.5°	175.7	190.1	204.5	252.1	339.5	495.3	729.5	993.6	1230.8	1386.6	1464.0
110°	196.5	210.4	224.3	269.0	344.4	477.4	673.0	910.2	1137.5	1320.1	1445.2

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	218.4	231.8	245.2	285.9	354.3	467.5	635.2	837.7	1045.2	1232.8	1376.7
115°	240.2	253.6	267.0	304.7	365.3	466.5	610.4	782.1	965.8	1138.5	1284.4
117.5°	262.0	274.4	286.9	324.6	379.2	467.5	593.6	745.4	904.2	1057.1	1191.1
120°	282.9	295.3	307.7	343.4	395.0	471.5	582.6	717.6	857.6	991.6	1110.7
122.5°	301.7	315.1	328.5	363.3	409.9	478.4	575.7	694.8	820.9	939.0	1047.2
125°	320.6	334.0	347.4	382.1	425.8	485.4	569.7	675.9	789.1	897.3	992.6
127.5°	338.5	351.9	365.3	399.0	438.7	493.3	566.8	658.1	760.3	858.6	945.9
130°	354.3	367.7	381.1	413.9	451.6	501.2	563.8	644.2	733.5	822.8	903.2
132.5°	369.2	382.1	395.0	426.8	463.5	507.2	562.8	631.3	708.7	789.1	862.5
135°	382.1	395.5	408.9	439.7	473.5	513.2	561.8	620.4	686.9	757.3	821.8
137.5°	394.0	406.4	418.9	448.6	481.4	517.1	559.8	610.4	666.0	725.6	783.1
140°	404.0	416.4	428.8	457.6	487.3	521.1	558.8	601.5	648.1	698.8	746.4
142.5°	413.9	425.3	436.7	464.5	493.3	524.1	556.8	593.6	631.3	673.0	712.7
145°	421.8	433.2	444.7	470.5	497.3	525.1	554.8	586.6	618.4	651.1	682.9
147.5°	431.8	441.7	451.6	475.4	500.3	525.1	551.9	579.7	607.4	634.2	661.0
150°	439.7	448.6	457.6	480.4	501.2	525.1	547.9	572.7	595.5	618.4	639.2
152.5°	447.6	456.0	464.5	483.4	503.2	522.1	542.9	564.8	584.6	603.5	621.3
155°	456.6	463.6	470.5	487.3	503.2	520.1	537.0	556.8	573.7	589.6	604.5
157.5°	464.5	470.0	475.4	489.3	504.2	517.1	532.0	547.9	561.8	575.7	587.6
160°	470.5	475.4	480.4	492.3	504.2	515.1	526.1	539.0	551.9	562.8	572.7
162.5°	475.4	479.4	483.4	493.3	503.2	511.2	520.1	530.0	540.0	548.9	557.8
165°	479.4	482.9	486.4	494.3	501.2	507.2	514.1	522.1	530.0	536.0	542.9
167.5°	483.4	485.8	488.3	494.3	500.3	503.2	508.2	514.1	521.1	526.1	530.0
170°	486.4	487.4	488.3	493.3	497.3	499.3	502.2	507.2	512.2	515.1	519.1
172.5°	488.3	488.8	489.3	493.3	496.3	496.3	497.3	500.3	504.2	506.2	509.2
175°	489.3	489.8	490.3	492.3	494.3	493.3	493.3	495.3	497.3	498.3	500.3
177.5°	490.3	490.3	490.3	491.3	493.3	491.3	490.3	491.3	492.3	493.3	494.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1746.9	1748.5	1743.7	1734.2	1732.6	1735.8	1745.3	1742.1	1734.2	1748.5	1735.8
5°	1650.4	1642.4	1639.3	1642.4	1633.0	1628.2	1637.7	1633.0	1637.7	1639.3	1644.0
7.5°	1557.0	1558.6	1549.1	1550.7	1538.0	1541.2	1541.2	1541.2	1545.9	1549.1	1555.4
10°	1476.3	1479.5	1468.4	1470.0	1460.5	1454.2	1458.9	1468.4	1468.4	1468.4	1471.6
12.5°	1411.4	1397.2	1389.3	1387.7	1376.6	1373.5	1382.9	1386.1	1394.0	1394.0	1398.8
15°	1330.7	1327.6	1321.2	1321.2	1294.3	1300.7	1303.8	1314.9	1330.7	1318.1	1321.2
17.5°	1257.9	1250.0	1242.1	1239.0	1235.8	1226.3	1239.0	1237.4	1246.9	1248.5	1253.2
20°	1193.1	1186.7	1170.9	1172.5	1175.7	1161.4	1169.3	1169.3	1178.8	1188.3	1199.4
22.5°	1129.8	1123.4	1115.5	1118.7	1109.2	1106.0	1106.0	1114.0	1125.0	1132.9	1131.4
25°	1080.7	1069.6	1064.9	1060.2	1055.4	1058.6	1053.8	1061.7	1069.6	1074.4	1069.6
27.5°	1025.3	1020.6	1011.1	1006.4	998.4	1001.6	1004.8	1011.1	1015.9	1015.9	1020.6
30°	971.5	965.2	962.1	957.3	957.3	951.0	952.6	958.9	963.6	968.4	974.7
32.5°	919.3	914.6	909.8	909.8	906.7	905.1	903.5	913.0	913.0	922.5	922.5
35°	876.6	868.7	868.7	860.8	863.9	862.4	859.2	865.5	867.1	873.4	871.9
37.5°	829.1	829.1	826.0	818.1	811.7	813.3	821.2	821.2	826.0	824.4	829.1
40°	781.7	778.5	778.5	773.8	772.2	770.6	772.2	773.8	781.7	780.1	781.7
42.5°	734.2	735.8	727.9	727.9	727.9	723.1	724.7	726.3	729.5	732.6	737.4
45°	688.3	685.1	683.6	680.4	677.2	678.8	677.2	683.6	682.0	685.1	689.9
47.5°	639.3	634.5	632.9	626.6	626.6	629.8	628.2	632.9	634.5	639.3	636.1
50°	591.8	585.5	580.7	582.3	572.8	576.0	576.0	580.7	585.5	587.0	590.2
52.5°	536.4	534.8	533.2	525.3	523.7	522.2	523.7	525.3	531.7	536.4	538.0
55°	482.6	481.0	471.5	468.4	463.6	463.6	466.8	468.4	479.4	481.0	487.4
57.5°	433.6	428.8	417.7	416.2	416.2	416.2	411.4	417.7	420.9	428.8	428.8
60°	379.8	379.8	370.3	370.3	371.8	370.3	370.3	371.8	371.8	378.2	381.3
62.5°	337.0	335.5	335.5	332.3	330.7	332.3	330.7	330.7	332.3	337.0	341.8
65°	299.1	297.5	295.9	294.3	291.1	291.1	292.7	295.9	295.9	299.1	300.6
67.5°	262.7	262.7	259.5	259.5	257.9	256.3	257.9	256.3	262.7	262.7	264.2
70°	226.3	224.7	219.9	218.4	213.6	215.2	215.2	219.9	221.5	224.7	227.9
72.5°	182.0	182.0	178.8	175.6	177.2	174.1	174.1	175.6	175.6	180.4	182.0
75°	150.3	147.2	145.6	147.2	145.6	148.7	145.6	145.6	148.7	148.7	148.7
77.5°	123.4	123.4	121.8	121.8	123.4	121.8	123.4	123.4	123.4	121.8	123.4
80°	101.3	99.7	99.7	99.7	98.1	98.1	98.1	98.1	98.1	98.1	98.1
82.5°	76.0	76.0	74.4	76.0	76.0	74.4	76.0	74.4	74.4	76.0	76.0
85°	50.6	53.8	50.6	50.6	52.2	52.2	53.8	52.2	53.8	50.6	52.2
87.5°	26.9	28.5	28.5	26.9	26.9	28.5	28.5	28.5	30.1	26.9	28.5
90°	27.8	28.8	27.8	28.8	29.8	28.8	29.8	28.8	27.8	28.8	27.8
92.5°	63.0	59.6	57.6	53.6	54.6	52.6	54.6	53.6	57.6	59.6	63.0
95°	171.7	153.8	135.0	126.1	119.1	115.1	119.1	126.1	135.0	153.8	171.7
97.5°	431.8	375.2	308.7	271.0	247.1	236.2	247.1	271.0	308.7	375.2	431.8
100°	903.2	832.8	732.5	660.1	621.3	622.3	621.3	660.1	732.5	832.8	903.2
102.5°	1209.4	1171.2	1098.8	1045.2	1014.4	985.6	1014.4	1045.2	1098.8	1171.2	1209.4
105°	1395.5	1382.6	1337.0	1299.3	1267.5	1262.5	1267.5	1299.3	1337.0	1382.6	1395.5
107.5°	1477.4	1490.8	1484.9	1467.0	1454.1	1443.2	1454.1	1467.0	1484.9	1490.8	1477.4
110°	1480.0	1514.7	1542.4	1550.4	1548.4	1546.4	1548.4	1550.4	1542.4	1514.7	1480.0

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1423.8	1471.0	1527.6	1556.3	1566.3	1567.3	1566.3	1556.3	1527.6	1471.0	1423.8
115°	1338.5	1392.6	1467.0	1510.7	1530.5	1535.5	1530.5	1510.7	1467.0	1392.6	1338.5
117.5°	1247.2	1303.2	1380.7	1429.3	1459.1	1466.0	1459.1	1429.3	1380.7	1303.2	1247.2
120°	1160.8	1210.9	1289.3	1344.9	1368.7	1374.7	1368.7	1344.9	1289.3	1210.9	1160.8
122.5°	1092.8	1138.5	1206.0	1254.6	1281.4	1289.3	1281.4	1254.6	1206.0	1138.5	1092.8
125°	1032.3	1072.0	1135.5	1179.2	1204.0	1210.9	1204.0	1179.2	1135.5	1072.0	1032.3
127.5°	982.6	1019.4	1076.9	1114.6	1137.5	1143.4	1137.5	1114.6	1076.9	1019.4	982.6
130°	937.0	970.7	1023.3	1059.1	1079.9	1087.8	1079.9	1059.1	1023.3	970.7	937.0
132.5°	894.3	926.1	974.7	1010.4	1028.3	1033.3	1028.3	1010.4	974.7	926.1	894.3
135°	850.1	878.4	927.1	956.8	974.7	981.6	974.7	956.8	927.1	878.4	850.1
137.5°	808.4	833.8	875.4	906.2	921.1	927.1	921.1	906.2	875.4	833.8	808.4
140°	767.8	789.1	826.8	854.6	870.5	869.5	870.5	854.6	826.8	789.1	767.8
142.5°	730.6	748.4	779.2	803.0	816.9	815.9	816.9	803.0	779.2	748.4	730.6
145°	697.3	711.7	736.5	757.3	765.3	767.3	765.3	757.3	736.5	711.7	697.3
147.5°	671.4	681.9	701.7	716.6	724.6	725.6	724.6	716.6	701.7	681.9	671.4
150°	648.7	658.1	673.0	683.9	689.8	689.8	689.8	683.9	673.0	658.1	648.7
152.5°	628.8	636.2	647.2	657.1	660.1	660.1	660.1	657.1	647.2	636.2	628.8
155°	610.4	616.4	625.3	633.3	635.2	636.2	635.2	633.3	625.3	616.4	610.4
157.5°	592.6	597.5	605.5	611.4	613.4	613.4	613.4	611.4	605.5	597.5	592.6
160°	576.2	579.7	586.6	592.6	592.6	591.6	592.6	592.6	586.6	579.7	576.2
162.5°	560.8	563.8	567.7	572.7	572.7	571.7	572.7	572.7	567.7	563.8	560.8
165°	545.4	547.9	551.9	555.8	554.8	554.8	554.8	555.8	551.9	547.9	545.4
167.5°	532.0	534.0	536.0	539.0	538.0	538.0	538.0	539.0	536.0	534.0	532.0
170°	520.1	521.1	522.1	524.1	523.1	523.1	523.1	524.1	522.1	521.1	520.1
172.5°	509.7	510.2	510.2	512.2	510.2	509.2	510.2	512.2	510.2	510.2	509.7
175°	500.3	500.3	500.3	501.2	500.3	499.3	500.3	501.2	500.3	500.3	500.3
177.5°	494.3	494.3	493.3	494.3	492.3	492.3	492.3	494.3	493.3	494.3	494.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2	1848.2
2.5°	1748.5	1754.8	1748.5	1735.8	1748.5	1756.4	1764.3	1776.9	1783.3	1783.3	1792.8
5°	1648.8	1661.4	1656.7	1653.5	1666.2	1674.1	1686.8	1702.6	1720.0	1731.1	1743.7
7.5°	1560.2	1568.1	1576.0	1576.0	1588.7	1606.1	1625.0	1644.0	1666.2	1682.0	1691.5
10°	1482.6	1489.0	1493.7	1500.0	1519.0	1538.0	1563.3	1587.1	1606.1	1623.5	1639.3
12.5°	1408.3	1417.8	1428.8	1433.6	1447.8	1471.6	1495.3	1523.8	1553.8	1571.2	1587.1
15°	1337.1	1341.8	1354.5	1368.7	1381.4	1406.7	1436.7	1466.8	1492.1	1519.0	1533.3
17.5°	1264.3	1265.9	1299.1	1291.2	1332.3	1356.0	1371.9	1400.4	1441.5	1463.6	1485.8
20°	1193.1	1208.9	1223.1	1231.0	1253.2	1280.1	1326.0	1348.1	1381.4	1401.9	1420.9
22.5°	1137.7	1161.4	1161.4	1180.4	1191.5	1216.8	1250.0	1292.8	1329.2	1343.4	1370.3
25°	1088.6	1099.7	1118.7	1125.0	1145.6	1167.8	1189.9	1235.8	1275.4	1294.3	1313.3
27.5°	1025.3	1039.6	1064.9	1064.9	1091.8	1115.5	1142.4	1172.5	1212.1	1239.0	1259.5
30°	976.3	990.5	1001.6	1019.0	1030.1	1052.2	1099.7	1121.9	1156.7	1180.4	1205.7
32.5°	930.4	941.5	951.0	970.0	982.6	1007.9	1033.3	1072.8	1102.9	1125.0	1151.9
35°	879.8	890.8	903.5	917.7	936.7	960.5	984.2	1017.4	1047.5	1068.1	1090.2
37.5°	832.3	840.2	859.2	868.7	884.5	906.7	936.7	971.5	998.4	1014.3	1036.4
40°	786.4	792.7	807.0	824.4	835.5	852.9	884.5	914.6	947.8	966.8	984.2
42.5°	737.4	745.3	757.9	775.3	792.7	811.7	829.1	863.9	894.0	909.8	928.8
45°	694.6	699.4	708.9	726.3	743.7	757.9	784.8	816.5	845.0	857.6	878.2
47.5°	644.0	648.8	663.0	670.9	689.9	708.9	735.8	767.4	792.7	805.4	824.4
50°	591.8	596.5	606.0	623.4	636.1	656.7	680.4	707.3	738.9	756.3	767.4
52.5°	541.2	550.6	558.6	572.8	588.6	609.2	631.3	656.7	683.6	701.0	713.6
55°	490.5	498.4	507.9	515.8	534.8	553.8	579.1	602.9	626.6	642.4	656.7
57.5°	433.6	444.6	454.1	469.9	484.2	500.0	528.5	547.5	576.0	587.0	599.7
60°	384.5	395.6	403.5	416.2	428.8	449.4	468.4	492.1	515.8	530.1	545.9
62.5°	343.4	348.1	352.9	365.5	378.2	397.2	416.2	439.9	465.2	473.1	485.8
65°	302.2	307.0	314.9	326.0	335.5	346.5	367.1	386.1	409.8	422.5	427.2
67.5°	267.4	272.2	273.7	281.7	289.6	302.2	313.3	332.3	354.4	362.4	371.8
70°	227.9	235.8	237.3	243.7	246.8	254.8	267.4	281.7	299.1	313.3	321.2
72.5°	182.0	193.0	196.2	205.7	210.4	218.4	227.9	238.9	250.0	256.3	262.7
75°	148.7	151.9	153.5	161.4	169.3	180.4	185.1	191.5	201.0	208.9	215.2
77.5°	123.4	125.0	126.6	126.6	128.2	134.5	144.0	151.9	158.2	161.4	166.1
80°	99.7	98.1	98.1	99.7	99.7	99.7	102.9	113.9	117.1	125.0	123.4
82.5°	77.5	74.4	76.0	74.4	74.4	74.4	74.4	76.0	76.0	80.7	83.9
85°	50.6	52.2	50.6	50.6	49.1	50.6	49.1	49.1	47.5	47.5	45.9
87.5°	26.9	28.5	26.9	26.9	25.3	26.9	25.3	25.3	23.7	23.7	20.6
90°	26.8	25.8	24.8	23.8	24.8	21.8	18.9	15.9	12.9	11.9	10.9
92.5°	66.5	76.4	98.3	138.0	184.6	204.5	152.9	100.2	68.5	59.6	50.6
95°	189.6	242.2	357.3	477.4	588.6	524.1	361.3	213.4	129.0	109.6	90.3
97.5°	488.3	619.4	820.9	936.0	905.2	675.9	402.0	230.3	146.9	125.6	104.2
100°	973.7	1089.8	1170.2	1135.5	940.0	635.2	374.2	227.3	157.8	138.4	119.1
102.5°	1247.7	1303.2	1286.4	1145.4	875.4	575.7	350.4	231.3	170.7	153.4	136.0
105°	1408.4	1389.6	1290.3	1082.9	798.0	529.0	341.4	239.2	185.6	170.2	154.8
107.5°	1464.0	1386.6	1230.8	993.6	729.5	495.3	339.5	252.1	204.5	190.1	175.7
110°	1445.2	1320.1	1137.5	910.2	673.0	477.4	344.4	269.0	224.3	210.4	196.5

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1376.7	1232.8	1045.2	837.7	635.2	467.5	354.3	285.9	245.2	231.8	218.4
115°	1284.4	1138.5	965.8	782.1	610.4	466.5	365.3	304.7	267.0	253.6	240.2
117.5°	1191.1	1057.1	904.2	745.4	593.6	467.5	379.2	324.6	286.9	274.4	262.0
120°	1110.7	991.6	857.6	717.6	582.6	471.5	395.0	343.4	307.7	295.3	282.9
122.5°	1047.2	939.0	820.9	694.8	575.7	478.4	409.9	363.3	328.5	315.1	301.7
125°	992.6	897.3	789.1	675.9	569.7	485.4	425.8	382.1	347.4	334.0	320.6
127.5°	945.9	858.6	760.3	658.1	566.8	493.3	438.7	399.0	365.3	351.9	338.5
130°	903.2	822.8	733.5	644.2	563.8	501.2	451.6	413.9	381.1	367.7	354.3
132.5°	862.5	789.1	708.7	631.3	562.8	507.2	463.5	426.8	395.0	382.1	369.2
135°	821.8	757.3	686.9	620.4	561.8	513.2	473.5	439.7	408.9	395.5	382.1
137.5°	783.1	725.6	666.0	610.4	559.8	517.1	481.4	448.6	418.9	406.4	394.0
140°	746.4	698.8	648.1	601.5	558.8	521.1	487.3	457.6	428.8	416.4	404.0
142.5°	712.7	673.0	631.3	593.6	556.8	524.1	493.3	464.5	436.7	425.3	413.9
145°	682.9	651.1	618.4	586.6	554.8	525.1	497.3	470.5	444.7	433.2	421.8
147.5°	661.0	634.2	607.4	579.7	551.9	525.1	500.3	475.4	451.6	441.7	431.8
150°	639.2	618.4	595.5	572.7	547.9	525.1	501.2	480.4	457.6	448.6	439.7
152.5°	621.3	603.5	584.6	564.8	542.9	522.1	503.2	483.4	464.5	456.0	447.6
155°	604.5	589.6	573.7	556.8	537.0	520.1	503.2	487.3	470.5	463.6	456.6
157.5°	587.6	575.7	561.8	547.9	532.0	517.1	504.2	489.3	475.4	470.0	464.5
160°	572.7	562.8	551.9	539.0	526.1	515.1	504.2	492.3	480.4	475.4	470.5
162.5°	557.8	548.9	540.0	530.0	520.1	511.2	503.2	493.3	483.4	479.4	475.4
165°	542.9	536.0	530.0	522.1	514.1	507.2	501.2	494.3	486.4	482.9	479.4
167.5°	530.0	526.1	521.1	514.1	508.2	503.2	500.3	494.3	488.3	485.8	483.4
170°	519.1	515.1	512.2	507.2	502.2	499.3	497.3	493.3	488.3	487.4	486.4
172.5°	509.2	506.2	504.2	500.3	497.3	496.3	496.3	493.3	489.3	488.8	488.3
175°	500.3	498.3	497.3	495.3	493.3	493.3	494.3	492.3	490.3	489.8	489.3
177.5°	494.3	493.3	492.3	491.3	490.3	491.3	493.3	491.3	490.3	490.3	490.3
180°	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3	490.3

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1848.2	1848.2	1848.2	1848.2
2.5°	1800.7	1811.8	1833.9	1852.9
5°	1762.7	1780.1	1813.3	1846.6
7.5°	1716.8	1743.7	1786.4	1832.3
10°	1672.5	1707.3	1759.5	1813.3
12.5°	1628.2	1664.6	1720.0	1789.6
15°	1576.0	1614.0	1680.4	1764.3
17.5°	1530.1	1580.7	1640.9	1724.7
20°	1481.1	1519.0	1596.6	1685.2
22.5°	1419.3	1482.6	1555.4	1648.8
25°	1370.3	1425.7	1498.5	1604.5
27.5°	1310.2	1375.0	1463.6	1557.0
30°	1261.1	1314.9	1397.2	1509.5
32.5°	1204.1	1267.4	1352.9	1463.6
35°	1153.5	1207.3	1288.0	1400.4
37.5°	1093.4	1151.9	1242.1	1341.8
40°	1041.2	1098.1	1183.6	1276.9
42.5°	977.9	1038.0	1123.4	1202.6
45°	927.2	982.6	1050.7	1123.4
47.5°	865.5	924.1	990.5	1041.2
50°	810.1	863.9	916.2	958.9
52.5°	750.0	799.1	846.5	878.2
55°	694.6	732.6	770.6	792.7
57.5°	629.8	666.2	697.8	710.5
60°	572.8	602.9	623.4	637.7
62.5°	512.7	534.8	550.6	558.6
65°	454.1	469.9	477.9	485.8
67.5°	394.0	408.2	413.0	422.5
70°	330.7	346.5	349.7	354.4
72.5°	283.2	283.2	289.6	295.9
75°	226.3	229.4	232.6	232.6
77.5°	177.2	177.2	180.4	182.0
80°	129.8	131.3	131.3	129.8
82.5°	88.6	91.8	88.6	87.0
85°	49.1	55.4	52.2	52.2
87.5°	20.6	20.6	23.7	20.6
90°	8.9	6.0	4.0	2.0
92.5°	40.7	31.8	21.8	14.9
95°	64.5	47.6	36.7	33.7
97.5°	78.4	63.5	54.6	53.6
100°	95.3	81.4	74.4	73.4
102.5°	115.1	102.2	96.3	94.3
105°	136.0	124.1	118.1	115.1
107.5°	157.8	145.9	140.0	137.0
110°	179.7	168.7	163.8	160.8

TEST NUMBER: P1012274

CATALOG NUMBER: S123RDIP-B1165D1025UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	201.5	190.6	185.6	182.6
115°	223.3	213.4	207.4	203.5
117.5°	243.2	234.2	229.3	224.3
120°	264.0	254.1	249.1	246.2
122.5°	283.9	273.0	268.0	265.0
125°	301.7	290.8	284.9	282.9
127.5°	317.6	306.7	299.8	296.8
130°	333.5	321.6	312.7	309.7
132.5°	348.4	333.5	323.6	319.6
135°	361.3	346.4	335.5	331.5
137.5°	373.2	357.3	346.4	342.4
140°	384.1	368.2	358.3	353.4
142.5°	394.0	380.2	369.2	365.3
145°	405.0	390.1	381.1	378.2
147.5°	414.9	402.0	393.1	391.1
150°	425.8	412.9	405.0	404.0
152.5°	435.7	424.8	416.9	416.9
155°	445.7	435.7	429.8	429.8
157.5°	454.6	445.7	440.7	439.7
160°	463.5	455.6	451.6	451.6
162.5°	469.5	463.5	460.5	460.5
165°	475.4	470.5	468.5	469.5
167.5°	480.4	476.4	475.4	476.4
170°	484.4	481.4	480.4	482.4
172.5°	487.3	485.4	485.4	486.4
175°	489.3	487.3	488.3	489.3
177.5°	490.3	489.3	490.3	491.3
180°	490.3	490.3	490.3	490.3

(END OF REPORT)