

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012356

Luminaire Tested: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012356
REPORT IS A COMBINATION OF REPORTS P993057 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6707.0 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	66	66	66
1	103	99	95	92	97	93	90	87	83	81	79	74	72	71	66	64	63	59	57	55
2	94	87	81	76	89	83	77	73	74	70	66	66	63	60	59	57	55	51	49	47
3	86	77	70	64	81	73	67	62	66	61	57	59	55	52	53	50	47	44	42	40
4	80	69	61	55	75	66	59	53	59	54	49	53	49	45	48	44	41	38	36	34
5	73	62	54	48	69	59	52	46	53	48	43	48	44	40	43	40	37	34	32	30
6	68	56	48	42	64	53	46	41	49	43	38	44	39	35	40	36	33	30	28	26
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	36	32	29	27	25	23
8	59	46	39	33	55	44	37	32	41	35	30	37	32	28	34	30	26	24	22	20
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	22	20	18
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19807	19807	19807	19807
5°	19822	22812	19873	16924
10°	19647	27538	19732	14782
15°	19445	31253	19445	13034
20°	19045	33712	19153	11563
25°	18754	32028	18718	10550
30°	18415	22191	18376	9560
35°	18006	14248	17925	8814
40°	17498	10061	17411	8071
45°	16613	8052	16589	7349
50°	15525	6735	15474	6503
55°	14302	5551	14187	5513
60°	13101	4588	12971	4689
65°	11693	3671	11768	3974
70°	10392	2550	10672	3213
75°	8810	1892	9168	2471
80°	7014	1255	7611	1853
85°	4995	594	5446	1153

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 26443 cd/sqm

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.7	2.7
10°-20°	565.7	8.4
20°-30°	890.9	13.3
30°-40°	926.4	13.8
40°-50°	792.6	11.8
50°-60°	604.3	9.0
60°-70°	387.1	5.8
70°-80°	185.5	2.8
80°-90°	50.3	0.8
90°-100°	153.2	2.3
100°-110°	448.5	6.7
110°-120°	437.9	6.5
120°-130°	348.8	5.2
130°-140°	275.2	4.1
140°-150°	205.3	3.1
150°-160°	143.1	2.1
160°-170°	84.1	1.3
170°-180°	27.3	0.4
0°-30°	1637.3	24.4
0°-40°	2563.8	38.2
0°-60°	3960.6	59.1
0°-90°	4583.6	68.3
90°-120°	1039.6	15.5
90°-150°	1868.9	27.9
90°-180°	2123.0	31.7
0°-180°	6707.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1840	1840	1840	1840	1840	
5°	1838	2185	1843	1621	1838	174
15°	1757	3105	1757	1295	1757	494
25°	1598	3200	1594	1054	1598	736
35°	1394	1388	1388	859	1394	873
45°	1119	740	1117	676	1119	861
55°	789	465	783	462	789	707
65°	484	268	487	290	484	483
75°	232	113	241	148	232	250
85°	52	27	57	52	52	58
90°	1	17	1	17	1	4
95°	19	66	19	66	19	21
105°	66	727	66	727	66	70
115°	117	884	117	884	117	116
125°	163	697	163	697	163	145
135°	191	565	191	565	191	147
145°	218	442	218	442	218	136
155°	247	366	247	366	247	114
165°	270	319	270	319	270	76
175°	282	287	282	287	282	27
180°	282	282	282	282	282	

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1844.8	1857.4	1866.9	1873.2	1889.0	1898.4	1906.3	1920.5	1920.5	1923.6	1929.9
5°	1838.5	1865.3	1884.2	1909.4	1942.5	1958.3	1980.3	1999.2	2026.0	2040.2	2054.4
7.5°	1824.4	1862.2	1901.6	1939.4	1988.2	2019.7	2041.8	2090.6	2125.3	2167.8	2200.9
10°	1805.5	1857.4	1907.9	1966.2	2032.3	2079.6	2112.7	2177.3	2243.4	2303.3	2353.7
12.5°	1781.8	1844.8	1917.3	1988.2	2081.2	2128.4	2182.0	2262.3	2356.9	2432.5	2500.2
15°	1756.6	1829.1	1911.0	1997.7	2114.2	2180.4	2257.6	2355.3	2460.8	2569.6	2662.5
17.5°	1717.2	1808.6	1900.0	2026.0	2163.1	2202.5	2268.6	2402.6	2533.3	2631.0	2744.4
20°	1677.8	1780.3	1895.3	2008.7	2156.8	2248.2	2309.6	2451.4	2591.6	2709.8	2818.5
22.5°	1641.6	1748.7	1868.5	2011.8	2150.5	2241.9	2319.1	2467.1	2629.4	2761.8	2895.7
25°	1597.5	1714.1	1846.4	1981.9	2150.5	2219.8	2304.9	2476.6	2648.3	2801.1	2966.6
27.5°	1550.2	1668.4	1799.2	1937.8	2092.2	2194.6	2278.1	2462.4	2672.0	2835.8	3005.9
30°	1503.0	1624.3	1750.3	1874.8	2048.1	2145.8	2241.9	2445.1	2684.6	2872.0	3002.8
32.5°	1457.3	1559.7	1684.2	1805.5	1977.2	2084.3	2193.0	2427.8	2689.3	2846.8	2909.8
35°	1394.3	1501.4	1602.2	1731.4	1904.7	2010.3	2137.9	2426.2	2668.8	2766.5	2735.0
37.5°	1336.0	1425.8	1521.9	1636.9	1814.9	1952.0	2084.3	2385.2	2601.1	2607.4	2429.3
40°	1271.4	1345.4	1425.8	1547.1	1739.3	1874.8	2018.1	2322.2	2478.2	2385.2	2071.7
42.5°	1197.3	1263.5	1326.5	1444.7	1654.2	1805.5	1959.9	2243.4	2300.1	2085.9	1759.8
45°	1118.6	1172.1	1230.4	1354.9	1564.4	1714.1	1868.5	2122.1	2063.8	1761.3	1451.0
47.5°	1036.6	1082.3	1139.0	1252.5	1468.3	1621.1	1767.6	1948.8	1800.7	1476.2	1216.2
50°	954.7	991.0	1046.1	1162.7	1370.6	1509.3	1644.8	1762.9	1555.0	1266.7	1005.1
52.5°	874.4	902.7	959.4	1058.7	1260.4	1392.7	1490.4	1536.1	1324.9	1046.1	872.8
55°	789.3	820.8	858.6	959.4	1159.5	1257.2	1321.8	1320.2	1102.8	887.0	721.6
57.5°	707.4	735.7	768.8	869.6	1031.9	1098.1	1153.2	1126.4	920.1	726.3	619.1
60°	634.9	650.7	686.9	772.0	894.9	951.6	983.1	937.4	751.5	612.8	512.0
62.5°	556.1	571.9	601.8	682.2	757.8	787.7	814.5	756.2	620.7	499.4	438.0
65°	483.7	504.1	523.0	587.6	628.6	664.8	661.7	612.8	485.2	406.5	356.1
67.5°	420.6	428.5	444.3	483.7	502.6	529.3	530.9	475.8	390.7	330.8	300.9
70°	352.9	360.8	371.8	390.7	403.3	409.6	406.5	357.6	294.6	258.4	231.6
72.5°	294.6	293.0	300.9	300.9	313.5	311.9	302.5	264.7	223.7	193.8	178.0
75°	231.6	233.2	234.7	231.6	226.9	220.6	212.7	184.3	157.5	143.4	129.2
77.5°	181.2	178.0	179.6	168.6	162.3	156.0	144.9	130.8	108.7	105.6	99.3
80°	129.2	127.6	126.0	121.3	107.1	100.8	93.0	85.1	80.3	77.2	75.6
82.5°	86.6	86.6	83.5	74.0	66.2	61.4	59.9	56.7	52.0	52.0	50.4
85°	52.0	50.4	47.3	37.8	33.1	33.1	33.1	33.1	29.9	29.9	28.4
87.5°	20.5	18.9	14.2	14.2	12.6	12.6	12.6	11.0	11.0	9.5	9.5
90°	1.1	2.3	3.4	5.1	6.3	6.8	7.4	9.1	10.9	12.6	14.3
92.5°	8.6	12.6	18.3	23.4	29.1	34.2	39.4	57.7	88.0	117.7	106.3
95°	19.4	21.1	27.4	37.1	52.0	63.2	74.3	122.9	208.0	301.7	338.9
97.5°	30.9	31.4	36.6	45.1	60.0	72.3	84.6	132.6	231.4	389.2	521.2
100°	42.3	42.9	46.9	54.9	68.6	79.8	90.9	130.9	215.4	365.7	541.2
102.5°	54.3	55.4	58.9	66.3	78.3	88.3	98.3	133.1	201.7	331.4	504.0
105°	66.3	68.0	71.4	78.3	89.1	98.0	106.9	137.7	196.6	304.6	459.4
107.5°	78.9	80.6	84.0	90.9	101.1	109.4	117.7	145.1	195.4	285.2	420.0
110°	92.6	94.3	97.1	103.4	113.1	121.1	129.1	154.9	198.3	274.9	387.4

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	105.1	106.9	109.7	116.0	125.7	133.4	141.1	164.6	204.0	269.1	365.7
115°	117.1	119.4	122.9	128.6	138.3	146.0	153.7	175.4	210.3	268.6	351.4
117.5°	129.1	132.0	134.9	140.0	150.9	158.0	165.1	186.9	218.3	269.1	341.7
120°	141.7	143.4	146.3	152.0	162.9	170.0	177.1	197.7	227.4	271.4	335.4
122.5°	152.6	154.3	157.1	163.4	173.7	181.4	189.1	209.1	236.0	275.4	331.4
125°	162.9	164.0	167.4	173.7	184.6	192.3	200.0	220.0	245.1	279.4	328.0
127.5°	170.9	172.6	176.6	182.9	194.9	202.6	210.3	229.7	252.6	284.0	326.3
130°	178.3	180.0	185.1	192.0	204.0	211.7	219.4	238.3	260.0	288.6	324.6
132.5°	184.0	186.3	192.0	200.6	212.6	220.0	227.4	245.7	266.9	292.0	324.0
135°	190.9	193.1	199.4	208.0	220.0	227.7	235.4	253.1	272.6	295.4	323.4
137.5°	197.1	199.4	205.7	214.9	226.9	234.0	241.1	258.3	277.2	297.7	322.3
140°	203.4	206.3	212.0	221.1	232.6	239.8	246.9	263.4	280.6	300.0	321.7
142.5°	210.3	212.6	218.9	226.9	238.3	244.8	251.4	267.4	284.0	301.7	320.6
145°	217.7	219.4	224.6	233.1	242.9	249.4	256.0	270.9	286.3	302.3	319.4
147.5°	225.1	226.3	231.4	238.9	248.6	254.3	260.0	273.7	288.0	302.3	317.7
150°	232.6	233.1	237.7	245.1	253.1	258.2	263.4	276.6	288.6	302.3	315.4
152.5°	240.0	240.0	244.6	250.9	257.7	262.5	267.4	278.3	289.7	300.6	312.6
155°	247.4	247.4	250.9	256.6	262.9	266.9	270.9	280.6	289.7	299.4	309.2
157.5°	253.1	253.7	256.6	261.7	267.4	270.5	273.7	281.7	290.3	297.7	306.3
160°	260.0	260.0	262.3	266.9	270.9	273.8	276.6	283.4	290.3	296.6	302.9
162.5°	265.1	265.1	266.9	270.3	273.7	276.0	278.3	284.0	289.7	294.3	299.4
165°	270.3	269.7	270.9	273.7	276.0	278.0	280.0	284.6	288.6	292.0	296.0
167.5°	274.3	273.7	274.3	276.6	278.3	279.8	281.2	284.6	288.0	289.7	292.6
170°	277.7	276.6	277.2	278.9	280.0	280.6	281.2	284.0	286.3	287.4	289.2
172.5°	280.0	279.4	279.4	280.6	281.2	281.4	281.7	284.0	285.7	285.7	286.3
175°	281.7	281.2	280.6	281.7	281.7	282.0	282.3	283.4	284.6	284.0	284.0
177.5°	282.9	282.3	281.7	282.3	282.3	282.3	282.3	282.9	284.0	282.9	282.3
180°	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1942.5	1942.5	1956.7	1970.9	1963.0	1967.7	1985.1	1978.8	1991.4	1989.8	1994.5
5°	2089.0	2106.4	2120.5	2150.5	2155.2	2150.5	2180.4	2188.3	2202.5	2185.1	2193.0
7.5°	2254.5	2290.7	2325.4	2369.5	2383.6	2386.8	2402.6	2424.6	2443.5	2408.9	2426.2
10°	2415.2	2470.3	2541.2	2580.6	2615.2	2627.8	2640.4	2654.6	2676.7	2697.2	2681.4
12.5°	2588.5	2668.8	2736.5	2807.4	2850.0	2845.3	2881.5	2890.9	2908.3	2913.0	2919.3
15°	2730.2	2843.7	2886.2	2991.8	3001.2	3032.7	3073.7	3109.9	3114.7	3105.2	3105.2
17.5°	2865.7	2963.4	3039.0	3124.1	3141.4	3168.2	3220.2	3237.5	3243.8	3242.3	3242.3
20°	2976.0	3040.6	3168.2	3239.1	3267.5	3302.1	3338.4	3360.4	3365.2	3371.5	3362.0
22.5°	3048.5	3146.2	3250.1	3308.4	3332.1	3344.7	3368.3	3374.6	3366.7	3368.3	3369.9
25°	3105.2	3201.3	3264.3	3280.1	3278.5	3262.7	3245.4	3215.5	3212.3	3199.7	3174.5
27.5°	3121.0	3157.2	3149.3	3084.7	3020.1	3013.8	2909.8	2853.1	2788.5	2798.0	2761.8
30°	3035.9	2988.6	2876.8	2712.9	2645.2	2534.9	2418.3	2297.0	2249.7	2197.7	2293.8
32.5°	2827.9	2659.4	2460.8	2248.2	2134.7	2037.1	1912.6	1824.4	1774.0	1731.4	1813.3
35°	2514.4	2251.3	1988.2	1786.6	1693.6	1605.4	1488.8	1444.7	1381.7	1388.0	1395.8
37.5°	2111.1	1821.2	1622.7	1424.2	1362.8	1326.5	1241.5	1173.7	1151.7	1145.3	1145.3
40°	1733.0	1495.1	1318.6	1162.7	1115.4	1085.5	1017.7	986.2	962.6	956.3	964.2
42.5°	1433.7	1230.4	1093.4	989.4	956.3	918.5	890.1	850.7	846.0	835.0	849.2
45°	1203.6	1027.2	924.8	849.2	820.8	806.6	775.1	751.5	742.0	740.5	751.5
47.5°	1020.9	883.8	794.0	746.8	724.7	710.5	683.7	674.3	664.8	668.0	663.3
50°	857.0	754.6	696.3	653.8	639.6	625.5	608.1	598.7	593.9	593.9	592.4
52.5°	735.7	650.7	612.8	573.5	567.2	559.3	540.4	534.1	526.2	524.6	530.9
55°	630.2	571.9	534.1	510.4	504.1	488.4	480.5	472.6	467.9	464.8	466.3
57.5°	538.8	494.7	469.5	449.0	438.0	431.7	417.5	415.9	412.8	412.8	411.2
60°	463.2	431.7	401.7	389.1	381.3	373.4	371.8	362.4	357.6	360.8	359.2
62.5°	392.3	367.1	349.7	335.6	330.8	324.5	319.8	316.7	311.9	313.5	313.5
65°	327.7	307.2	294.6	282.0	280.4	274.1	272.6	269.4	269.4	267.8	271.0
67.5°	269.4	255.2	244.2	236.3	231.6	233.2	226.9	222.1	222.1	220.6	225.3
70°	214.3	206.4	195.4	185.9	179.6	179.6	171.7	170.1	170.1	170.1	168.6
72.5°	165.4	151.2	146.5	143.4	143.4	143.4	140.2	140.2	138.6	140.2	138.6
75°	122.9	121.3	118.2	116.6	116.6	115.0	113.4	113.4	113.4	113.4	113.4
77.5°	96.1	96.1	93.0	91.4	91.4	91.4	89.8	89.8	88.2	88.2	88.2
80°	70.9	70.9	67.7	67.7	67.7	66.2	66.2	66.2	67.7	66.2	66.2
82.5°	48.8	48.8	47.3	48.8	47.3	45.7	45.7	45.7	44.1	45.7	45.7
85°	28.4	28.4	26.8	25.2	26.8	26.8	25.2	26.8	25.2	26.8	25.2
87.5°	11.0	9.5	9.5	9.5	7.9	9.5	7.9	7.9	9.5	7.9	9.5
90°	13.7	14.3	14.9	15.4	16.0	16.6	16.0	16.6	17.1	16.6	17.1
92.5°	79.4	56.6	44.0	38.3	36.3	34.3	33.1	30.9	31.4	30.3	31.4
95°	274.9	205.7	139.4	109.1	98.8	88.6	77.7	72.6	68.6	66.3	68.6
97.5°	538.9	472.6	356.6	281.2	248.6	216.0	177.7	156.0	142.3	136.0	142.3
100°	653.7	673.7	627.4	560.6	520.0	479.4	421.7	380.0	357.7	358.3	357.7
102.5°	659.4	740.6	750.3	718.3	696.3	674.3	632.6	601.7	584.0	567.4	584.0
105°	623.4	742.9	800.0	810.9	803.4	796.0	769.7	748.0	729.7	726.9	729.7
107.5°	572.0	708.6	798.3	842.9	850.6	858.3	854.9	844.6	837.2	830.9	837.2
110°	524.0	654.9	760.0	832.0	852.0	872.0	888.0	892.6	891.5	890.3	891.5

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	482.3	601.7	709.7	792.6	819.8	846.9	879.5	896.0	901.7	902.3	901.7
115°	450.3	556.0	655.4	739.4	770.6	801.7	844.6	869.7	881.2	884.0	881.2
117.5°	429.2	520.6	608.6	685.7	718.0	750.3	794.9	822.9	840.0	844.0	840.0
120°	413.2	493.7	570.9	639.4	668.3	697.2	742.3	774.3	788.0	791.4	788.0
122.5°	400.0	472.6	540.6	602.9	629.2	655.4	694.3	722.3	737.7	742.3	737.7
125°	389.2	454.3	516.6	571.4	594.3	617.2	653.7	678.9	693.2	697.2	693.2
127.5°	378.9	437.7	494.3	544.6	565.8	586.9	620.0	641.7	654.9	658.3	654.9
130°	370.9	422.3	473.7	520.0	539.4	558.9	589.2	609.7	621.7	626.3	621.7
132.5°	363.4	408.0	454.3	496.6	514.9	533.2	561.2	581.7	592.0	594.9	592.0
135°	357.2	395.4	436.0	473.2	489.4	505.7	533.7	550.9	561.2	565.2	561.2
137.5°	351.4	383.4	417.7	450.9	465.4	480.0	504.0	521.7	530.3	533.7	530.3
140°	346.3	373.2	402.3	429.7	442.0	454.3	476.0	492.0	501.2	500.6	501.2
142.5°	341.7	363.4	387.4	410.3	420.6	430.9	448.6	462.3	470.3	469.7	470.3
145°	337.7	356.0	374.9	393.2	401.4	409.7	424.0	436.0	440.6	441.7	440.6
147.5°	333.7	349.7	365.2	380.6	386.6	392.6	404.0	412.6	417.2	417.7	417.2
150°	329.7	342.9	356.0	368.0	373.4	378.9	387.4	393.7	397.2	397.2	397.2
152.5°	325.2	336.6	347.4	357.7	362.0	366.3	372.6	378.3	380.0	380.0	380.0
155°	320.6	330.3	339.4	348.0	351.4	354.9	360.0	364.6	365.7	366.3	365.7
157.5°	315.4	323.4	331.4	338.3	341.2	344.0	348.6	352.0	353.2	353.2	353.2
160°	310.3	317.7	324.0	329.7	331.7	333.7	337.7	341.2	341.2	340.6	341.2
162.5°	305.2	310.9	316.0	321.2	322.9	324.6	326.9	329.7	329.7	329.2	329.7
165°	300.6	305.2	308.6	312.6	314.0	315.4	317.7	320.0	319.4	319.4	319.4
167.5°	296.0	300.0	302.9	305.2	306.3	307.4	308.6	310.3	309.7	309.7	309.7
170°	292.0	294.9	296.6	298.9	299.4	300.0	300.6	301.7	301.2	301.2	301.2
172.5°	288.0	290.3	291.4	293.2	293.4	293.7	293.7	294.9	293.7	293.2	293.7
175°	285.2	286.3	286.9	288.0	288.0	288.0	288.0	288.6	288.0	287.4	288.0
177.5°	282.9	283.4	284.0	284.6	284.6	284.6	284.0	284.6	283.4	283.4	283.4
180°	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1986.6	1977.2	1970.9	1966.2	1961.4	1975.6	1956.7	1936.2	1922.0	1912.6	1909.4
5°	2194.6	2174.1	2156.8	2142.6	2145.8	2145.8	2112.7	2076.4	2044.9	2027.6	2008.7
7.5°	2435.6	2413.6	2378.9	2371.0	2364.7	2325.4	2292.3	2226.1	2186.7	2147.3	2112.7
10°	2675.1	2646.7	2613.7	2602.6	2586.9	2538.0	2487.6	2402.6	2353.7	2281.2	2235.6
12.5°	2898.8	2864.2	2831.1	2823.2	2799.6	2757.0	2670.4	2582.2	2498.7	2421.5	2341.1
15°	3086.3	3076.8	3026.4	2994.9	2942.9	2884.6	2865.7	2746.0	2640.4	2560.1	2415.2
17.5°	3243.8	3199.7	3152.5	3132.0	3111.5	3043.8	2976.0	2853.1	2739.7	2621.5	2528.6
20°	3369.9	3321.0	3288.0	3258.0	3248.6	3171.4	3064.2	2955.5	2831.1	2698.7	2577.4
22.5°	3376.2	3369.9	3347.8	3330.5	3311.6	3261.2	3176.1	3040.6	2908.3	2763.3	2604.2
25°	3245.4	3236.0	3299.0	3283.2	3295.8	3276.9	3231.2	3117.8	2963.4	2793.3	2632.6
27.5°	2851.6	2947.7	3046.9	3081.6	3105.2	3172.9	3195.0	3132.0	3007.5	2826.3	2646.7
30°	2315.9	2443.5	2604.2	2690.9	2757.0	2883.1	3046.9	3067.4	3009.1	2864.2	2643.6
32.5°	1818.1	1934.6	2063.8	2166.2	2254.5	2512.8	2733.4	2892.5	2920.9	2845.3	2651.5
35°	1465.2	1515.6	1638.5	1736.1	1855.9	2076.4	2336.4	2593.2	2766.5	2775.9	2627.8
37.5°	1208.4	1235.1	1342.3	1397.4	1468.3	1662.1	1904.7	2240.3	2509.7	2637.3	2561.7
40°	1000.4	1061.8	1123.3	1154.8	1205.2	1339.1	1572.3	1835.4	2169.4	2405.7	2459.3
42.5°	868.1	894.9	934.2	978.4	1009.9	1126.4	1282.4	1523.5	1824.4	2153.6	2301.7
45°	765.7	775.1	816.1	844.4	877.5	959.4	1069.7	1271.4	1536.1	1860.6	2112.7
47.5°	680.6	699.5	721.6	738.9	760.9	824.0	918.5	1065.0	1298.2	1588.0	1859.0
50°	605.0	616.0	644.4	652.2	668.0	712.1	784.6	896.4	1088.6	1320.2	1600.7
52.5°	534.1	554.6	565.6	576.6	590.8	627.0	674.3	765.7	910.6	1128.0	1365.9
55°	478.9	485.2	501.0	510.4	521.5	546.7	587.6	655.4	768.8	942.1	1167.4
57.5°	425.4	425.4	441.1	449.0	460.0	478.9	515.2	567.2	649.1	778.3	984.7
60°	368.7	370.2	382.8	392.3	395.4	414.3	444.3	485.2	548.3	642.8	811.4
62.5°	318.2	326.1	332.4	335.6	346.6	357.6	382.8	411.2	455.3	538.8	658.5
65°	275.7	277.3	282.0	285.2	289.9	302.5	321.4	340.3	378.1	439.5	537.2
67.5°	226.9	233.2	239.5	239.5	244.2	250.5	269.4	285.2	313.5	349.7	415.9
70°	170.1	173.3	182.8	187.5	193.8	204.8	214.3	223.7	245.8	272.6	323.0
72.5°	141.8	141.8	144.9	146.5	146.5	154.4	168.6	178.0	189.1	208.0	242.6
75°	113.4	113.4	118.2	116.6	119.7	122.9	124.5	130.8	137.1	151.2	171.7
77.5°	89.8	91.4	91.4	93.0	93.0	94.5	96.1	99.3	102.4	110.3	119.7
80°	66.2	67.7	67.7	69.3	69.3	70.9	72.5	74.0	77.2	80.3	85.1
82.5°	45.7	47.3	47.3	48.8	47.3	48.8	50.4	50.4	52.0	55.1	56.7
85°	26.8	26.8	28.4	26.8	26.8	26.8	28.4	28.4	29.9	34.7	34.7
87.5°	7.9	9.5	7.9	9.5	9.5	9.5	9.5	11.0	11.0	12.6	14.2
90°	16.6	16.0	16.6	16.0	15.4	14.9	14.3	13.7	14.3	12.6	10.9
92.5°	30.9	33.1	34.3	36.3	38.3	44.0	56.6	79.4	106.3	117.7	88.0
95°	72.6	77.7	88.6	98.8	109.1	139.4	205.7	274.9	338.9	301.7	208.0
97.5°	156.0	177.7	216.0	248.6	281.2	356.6	472.6	538.9	521.2	389.2	231.4
100°	380.0	421.7	479.4	520.0	560.6	627.4	673.7	653.7	541.2	365.7	215.4
102.5°	601.7	632.6	674.3	696.3	718.3	750.3	740.6	659.4	504.0	331.4	201.7
105°	748.0	769.7	796.0	803.4	810.9	800.0	742.9	623.4	459.4	304.6	196.6
107.5°	844.6	854.9	858.3	850.6	842.9	798.3	708.6	572.0	420.0	285.2	195.4
110°	892.6	888.0	872.0	852.0	832.0	760.0	654.9	524.0	387.4	274.9	198.3

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	896.0	879.5	846.9	819.8	792.6	709.7	601.7	482.3	365.7	269.1	204.0
115°	869.7	844.6	801.7	770.6	739.4	655.4	556.0	450.3	351.4	268.6	210.3
117.5°	822.9	794.9	750.3	718.0	685.7	608.6	520.6	429.2	341.7	269.1	218.3
120°	774.3	742.3	697.2	668.3	639.4	570.9	493.7	413.2	335.4	271.4	227.4
122.5°	722.3	694.3	655.4	629.2	602.9	540.6	472.6	400.0	331.4	275.4	236.0
125°	678.9	653.7	617.2	594.3	571.4	516.6	454.3	389.2	328.0	279.4	245.1
127.5°	641.7	620.0	586.9	565.8	544.6	494.3	437.7	378.9	326.3	284.0	252.6
130°	609.7	589.2	558.9	539.4	520.0	473.7	422.3	370.9	324.6	288.6	260.0
132.5°	581.7	561.2	533.2	514.9	496.6	454.3	408.0	363.4	324.0	292.0	266.9
135°	550.9	533.7	505.7	489.4	473.2	436.0	395.4	357.2	323.4	295.4	272.6
137.5°	521.7	504.0	480.0	465.4	450.9	417.7	383.4	351.4	322.3	297.7	277.2
140°	492.0	476.0	454.3	442.0	429.7	402.3	373.2	346.3	321.7	300.0	280.6
142.5°	462.3	448.6	430.9	420.6	410.3	387.4	363.4	341.7	320.6	301.7	284.0
145°	436.0	424.0	409.7	401.4	393.2	374.9	356.0	337.7	319.4	302.3	286.3
147.5°	412.6	404.0	392.6	386.6	380.6	365.2	349.7	333.7	317.7	302.3	288.0
150°	393.7	387.4	378.9	373.4	368.0	356.0	342.9	329.7	315.4	302.3	288.6
152.5°	378.3	372.6	366.3	362.0	357.7	347.4	336.6	325.2	312.6	300.6	289.7
155°	364.6	360.0	354.9	351.4	348.0	339.4	330.3	320.6	309.2	299.4	289.7
157.5°	352.0	348.6	344.0	341.2	338.3	331.4	323.4	315.4	306.3	297.7	290.3
160°	341.2	337.7	333.7	331.7	329.7	324.0	317.7	310.3	302.9	296.6	290.3
162.5°	329.7	326.9	324.6	322.9	321.2	316.0	310.9	305.2	299.4	294.3	289.7
165°	320.0	317.7	315.4	314.0	312.6	308.6	305.2	300.6	296.0	292.0	288.6
167.5°	310.3	308.6	307.4	306.3	305.2	302.9	300.0	296.0	292.6	289.7	288.0
170°	301.7	300.6	300.0	299.4	298.9	296.6	294.9	292.0	289.2	287.4	286.3
172.5°	294.9	293.7	293.7	293.4	293.2	291.4	290.3	288.0	286.3	285.7	285.7
175°	288.6	288.0	288.0	288.0	288.0	286.9	286.3	285.2	284.0	284.0	284.6
177.5°	284.6	284.0	284.6	284.6	284.6	284.0	283.4	282.9	282.3	282.9	284.0
180°	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1904.7	1896.8	1889.0	1889.0	1871.6	1855.9	1848.0	1851.1	1841.7	1829.1	1816.5
5°	1988.2	1956.7	1950.4	1933.1	1909.4	1876.4	1859.0	1843.3	1824.4	1799.2	1775.5
7.5°	2065.4	2024.4	2002.4	1985.1	1939.4	1893.7	1855.9	1830.7	1797.6	1759.8	1731.4
10°	2166.2	2090.6	2067.0	2027.6	1963.0	1898.4	1854.3	1813.3	1767.6	1723.5	1685.7
12.5°	2246.6	2159.9	2115.8	2076.4	1992.9	1911.0	1837.0	1786.6	1731.4	1682.6	1633.7
15°	2338.0	2240.3	2163.1	2115.8	2010.3	1911.0	1827.5	1756.6	1695.2	1635.3	1592.8
17.5°	2382.1	2259.2	2224.5	2156.8	2004.0	1904.7	1802.3	1726.7	1652.6	1583.3	1532.9
20°	2451.4	2308.0	2221.4	2175.7	2040.2	1893.7	1774.0	1687.3	1610.1	1536.1	1482.5
22.5°	2456.1	2300.1	2243.4	2156.8	1989.8	1860.6	1748.7	1643.2	1553.4	1484.1	1428.9
25°	2445.1	2286.0	2207.2	2137.9	1999.2	1841.7	1698.3	1594.4	1506.1	1425.8	1361.2
27.5°	2440.4	2245.0	2171.0	2101.6	1945.7	1786.6	1668.4	1550.2	1449.4	1378.5	1312.3
30°	2434.1	2200.9	2111.1	2030.7	1887.4	1744.0	1602.2	1499.8	1403.7	1313.9	1247.8
32.5°	2393.1	2141.0	2049.7	1964.6	1810.2	1666.8	1555.0	1446.3	1342.3	1258.8	1198.9
35°	2380.5	2085.9	1966.2	1874.8	1723.5	1595.9	1477.8	1388.0	1290.3	1206.8	1135.9
37.5°	2344.3	2029.2	1900.0	1783.4	1625.9	1504.6	1417.9	1328.1	1233.6	1143.8	1087.1
40°	2281.2	1963.0	1816.5	1696.8	1534.5	1411.6	1331.3	1265.1	1172.1	1091.8	1022.5
42.5°	2188.3	1895.3	1737.7	1611.7	1432.1	1317.1	1250.9	1187.9	1109.1	1025.6	968.9
45°	2081.2	1805.5	1658.9	1518.7	1336.0	1224.1	1154.8	1117.0	1044.5	973.6	907.5
47.5°	1934.6	1712.5	1567.6	1422.6	1236.7	1128.0	1072.9	1035.1	984.7	907.5	853.9
50°	1750.3	1592.8	1455.7	1326.5	1139.0	1035.1	979.9	951.6	909.0	853.9	801.9
52.5°	1545.5	1454.1	1340.7	1221.0	1039.8	942.1	891.7	869.6	838.1	786.1	742.0
55°	1339.1	1299.7	1222.5	1104.4	935.8	855.5	811.4	783.0	759.4	721.6	683.7
57.5°	1154.8	1135.9	1082.3	991.0	849.2	765.7	727.9	709.0	690.0	661.7	623.9
60°	964.2	984.7	929.5	883.8	754.6	682.2	649.1	628.6	619.1	593.9	570.3
62.5°	798.8	817.7	786.1	751.5	660.1	595.5	575.0	556.1	549.8	527.8	504.1
65°	649.1	672.7	649.1	630.2	575.0	521.5	496.3	486.8	480.5	466.3	447.4
67.5°	516.7	540.4	529.3	505.7	488.4	444.3	430.1	420.6	417.5	406.5	390.7
70°	389.1	422.2	425.4	411.2	395.4	375.0	365.5	362.4	354.5	345.0	335.6
72.5°	280.4	318.2	319.8	319.8	310.4	310.4	300.9	296.2	296.2	286.7	275.7
75°	206.4	231.6	234.7	237.9	242.6	247.3	241.0	241.0	239.5	230.0	225.3
77.5°	137.1	159.1	167.0	178.0	184.3	184.3	187.5	190.6	187.5	182.8	179.6
80°	88.2	104.0	113.4	119.7	129.2	133.9	138.6	140.2	137.1	135.5	130.8
82.5°	58.3	63.0	67.7	75.6	86.6	94.5	94.5	93.0	96.1	94.5	93.0
85°	33.1	36.2	37.8	39.4	45.7	53.6	55.1	56.7	59.9	56.7	53.6
87.5°	12.6	14.2	14.2	14.2	17.3	18.9	23.6	29.9	28.4	25.2	25.2
90°	9.1	7.4	6.8	6.3	5.1	3.4	2.3	1.1	2.3	3.4	5.1
92.5°	57.7	39.4	34.2	29.1	23.4	18.3	12.6	8.6	12.6	18.3	23.4
95°	122.9	74.3	63.2	52.0	37.1	27.4	21.1	19.4	21.1	27.4	37.1
97.5°	132.6	84.6	72.3	60.0	45.1	36.6	31.4	30.9	31.4	36.6	45.1
100°	130.9	90.9	79.8	68.6	54.9	46.9	42.9	42.3	42.9	46.9	54.9
102.5°	133.1	98.3	88.3	78.3	66.3	58.9	55.4	54.3	55.4	58.9	66.3
105°	137.7	106.9	98.0	89.1	78.3	71.4	68.0	66.3	68.0	71.4	78.3
107.5°	145.1	117.7	109.4	101.1	90.9	84.0	80.6	78.9	80.6	84.0	90.9
110°	154.9	129.1	121.1	113.1	103.4	97.1	94.3	92.6	94.3	97.1	103.4

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	164.6	141.1	133.4	125.7	116.0	109.7	106.9	105.1	106.9	109.7	116.0
115°	175.4	153.7	146.0	138.3	128.6	122.9	119.4	117.1	119.4	122.9	128.6
117.5°	186.9	165.1	158.0	150.9	140.0	134.9	132.0	129.1	132.0	134.9	140.0
120°	197.7	177.1	170.0	162.9	152.0	146.3	143.4	141.7	143.4	146.3	152.0
122.5°	209.1	189.1	181.4	173.7	163.4	157.1	154.3	152.6	154.3	157.1	163.4
125°	220.0	200.0	192.3	184.6	173.7	167.4	164.0	162.9	164.0	167.4	173.7
127.5°	229.7	210.3	202.6	194.9	182.9	176.6	172.6	170.9	172.6	176.6	182.9
130°	238.3	219.4	211.7	204.0	192.0	185.1	180.0	178.3	180.0	185.1	192.0
132.5°	245.7	227.4	220.0	212.6	200.6	192.0	186.3	184.0	186.3	192.0	200.6
135°	253.1	235.4	227.7	220.0	208.0	199.4	193.1	190.9	193.1	199.4	208.0
137.5°	258.3	241.1	234.0	226.9	214.9	205.7	199.4	197.1	199.4	205.7	214.9
140°	263.4	246.9	239.8	232.6	221.1	212.0	206.3	203.4	206.3	212.0	221.1
142.5°	267.4	251.4	244.8	238.3	226.9	218.9	212.6	210.3	212.6	218.9	226.9
145°	270.9	256.0	249.4	242.9	233.1	224.6	219.4	217.7	219.4	224.6	233.1
147.5°	273.7	260.0	254.3	248.6	238.9	231.4	226.3	225.1	226.3	231.4	238.9
150°	276.6	263.4	258.2	253.1	245.1	237.7	233.1	232.6	233.1	237.7	245.1
152.5°	278.3	267.4	262.5	257.7	250.9	244.6	240.0	240.0	240.0	244.6	250.9
155°	280.6	270.9	266.9	262.9	256.6	250.9	247.4	247.4	247.4	250.9	256.6
157.5°	281.7	273.7	270.5	267.4	261.7	256.6	253.7	253.1	253.7	256.6	261.7
160°	283.4	276.6	273.8	270.9	266.9	262.3	260.0	260.0	260.0	262.3	266.9
162.5°	284.0	278.3	276.0	273.7	270.3	266.9	265.1	265.1	265.1	266.9	270.3
165°	284.6	280.0	278.0	276.0	273.7	270.9	269.7	270.3	269.7	270.9	273.7
167.5°	284.6	281.2	279.8	278.3	276.6	274.3	273.7	274.3	273.7	274.3	276.6
170°	284.0	281.2	280.6	280.0	278.9	277.2	276.6	277.7	276.6	277.2	278.9
172.5°	284.0	281.7	281.4	281.2	280.6	279.4	279.4	280.0	279.4	279.4	280.6
175°	283.4	282.3	282.0	281.7	281.7	280.6	281.2	281.7	281.2	280.6	281.7
177.5°	282.9	282.3	282.3	282.3	282.3	281.7	282.3	282.9	282.3	281.7	282.3
180°	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1816.5	1808.6	1805.5	1797.6	1778.7	1766.1	1751.9	1742.4	1744.0	1736.1	1740.9
5°	1759.8	1758.2	1747.2	1731.4	1704.6	1690.5	1665.2	1652.6	1646.3	1647.9	1638.5
7.5°	1712.5	1698.3	1690.5	1665.2	1640.0	1610.1	1589.6	1578.6	1569.1	1559.7	1553.4
10°	1658.9	1646.3	1633.7	1607.0	1572.3	1543.9	1515.6	1504.6	1490.4	1484.1	1479.3
12.5°	1602.2	1594.4	1578.6	1547.1	1507.7	1480.9	1447.8	1441.5	1422.6	1410.0	1406.9
15°	1550.2	1545.5	1517.2	1480.9	1441.5	1414.7	1386.4	1367.5	1336.0	1342.3	1331.3
17.5°	1495.1	1474.6	1457.3	1408.4	1389.5	1348.6	1315.5	1306.0	1284.0	1269.8	1255.6
20°	1433.7	1421.1	1399.0	1367.5	1321.8	1274.5	1249.3	1233.6	1221.0	1198.9	1192.6
22.5°	1375.4	1359.6	1340.7	1299.7	1260.4	1221.0	1186.3	1172.1	1156.4	1140.6	1131.2
25°	1329.7	1306.0	1285.6	1235.1	1195.8	1162.7	1140.6	1117.0	1094.9	1085.5	1082.3
27.5°	1258.8	1244.6	1224.1	1176.9	1140.6	1104.4	1083.9	1068.2	1044.5	1033.5	1024.0
30°	1213.1	1184.7	1161.1	1123.3	1087.1	1047.7	1028.8	1009.9	995.7	981.5	970.5
32.5°	1151.7	1129.6	1110.7	1072.9	1036.6	1000.4	979.9	951.6	943.7	932.7	920.1
35°	1091.8	1077.6	1057.1	1016.2	976.8	951.6	929.5	902.7	893.3	885.4	874.4
37.5°	1035.1	1014.6	1000.4	961.0	926.4	896.4	879.1	857.0	850.7	841.3	833.4
40°	986.2	965.7	951.6	912.2	875.9	844.4	833.4	811.4	801.9	790.9	786.1
42.5°	931.1	913.8	894.9	866.5	828.7	797.2	775.1	762.5	749.9	745.2	735.7
45°	872.8	857.0	842.9	811.4	772.0	749.9	731.0	713.7	704.2	696.3	690.0
47.5°	822.4	808.2	789.3	754.6	723.1	702.6	683.7	666.4	657.0	647.5	639.6
50°	764.1	756.2	735.7	702.6	672.7	649.1	631.8	616.0	609.7	598.7	586.1
52.5°	712.1	697.9	680.6	653.8	627.0	598.7	575.0	565.6	554.6	548.3	537.2
55°	650.7	641.2	622.3	598.7	570.3	546.7	529.3	516.7	502.6	496.3	482.1
57.5°	598.7	581.3	571.9	542.0	515.2	491.5	478.9	466.3	450.6	441.1	434.8
60°	542.0	526.2	512.0	486.8	467.9	442.7	423.8	412.8	401.7	389.1	382.8
62.5°	486.8	474.2	456.9	436.4	412.8	392.3	378.1	362.4	356.1	343.4	338.7
65°	426.9	417.5	403.3	379.7	360.8	343.4	329.3	316.7	310.4	305.6	302.5
67.5°	373.4	360.8	351.3	330.8	310.4	296.2	288.3	280.4	272.6	267.8	263.1
70°	318.2	308.8	299.3	280.4	266.3	253.6	247.3	241.0	236.3	231.6	226.9
72.5°	261.5	256.8	247.3	234.7	223.7	214.3	209.5	201.7	196.9	189.1	185.9
75°	215.8	208.0	203.2	192.2	182.8	174.9	168.6	159.1	152.8	149.7	148.1
77.5°	170.1	167.0	160.7	151.2	146.5	138.6	129.2	126.0	122.9	122.9	121.3
80°	127.6	122.9	118.2	110.3	105.6	99.3	99.3	99.3	97.7	99.3	97.7
82.5°	86.6	83.5	80.3	75.6	74.0	74.0	75.6	75.6	75.6	75.6	75.6
85°	50.4	50.4	50.4	52.0	50.4	50.4	52.0	53.6	52.0	52.0	50.4
87.5°	23.6	23.6	25.2	25.2	26.8	26.8	26.8	26.8	26.8	26.8	28.4
90°	6.3	6.8	7.4	9.1	10.9	12.6	14.3	13.7	14.3	14.9	15.4
92.5°	29.1	34.2	39.4	57.7	88.0	117.7	106.3	79.4	56.6	44.0	38.3
95°	52.0	63.2	74.3	122.9	208.0	301.7	338.9	274.9	205.7	139.4	109.1
97.5°	60.0	72.3	84.6	132.6	231.4	389.2	521.2	538.9	472.6	356.6	281.2
100°	68.6	79.8	90.9	130.9	215.4	365.7	541.2	653.7	673.7	627.4	560.6
102.5°	78.3	88.3	98.3	133.1	201.7	331.4	504.0	659.4	740.6	750.3	718.3
105°	89.1	98.0	106.9	137.7	196.6	304.6	459.4	623.4	742.9	800.0	810.9
107.5°	101.1	109.4	117.7	145.1	195.4	285.2	420.0	572.0	708.6	798.3	842.9
110°	113.1	121.1	129.1	154.9	198.3	274.9	387.4	524.0	654.9	760.0	832.0

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	125.7	133.4	141.1	164.6	204.0	269.1	365.7	482.3	601.7	709.7	792.6
115°	138.3	146.0	153.7	175.4	210.3	268.6	351.4	450.3	556.0	655.4	739.4
117.5°	150.9	158.0	165.1	186.9	218.3	269.1	341.7	429.2	520.6	608.6	685.7
120°	162.9	170.0	177.1	197.7	227.4	271.4	335.4	413.2	493.7	570.9	639.4
122.5°	173.7	181.4	189.1	209.1	236.0	275.4	331.4	400.0	472.6	540.6	602.9
125°	184.6	192.3	200.0	220.0	245.1	279.4	328.0	389.2	454.3	516.6	571.4
127.5°	194.9	202.6	210.3	229.7	252.6	284.0	326.3	378.9	437.7	494.3	544.6
130°	204.0	211.7	219.4	238.3	260.0	288.6	324.6	370.9	422.3	473.7	520.0
132.5°	212.6	220.0	227.4	245.7	266.9	292.0	324.0	363.4	408.0	454.3	496.6
135°	220.0	227.7	235.4	253.1	272.6	295.4	323.4	357.2	395.4	436.0	473.2
137.5°	226.9	234.0	241.1	258.3	277.2	297.7	322.3	351.4	383.4	417.7	450.9
140°	232.6	239.8	246.9	263.4	280.6	300.0	321.7	346.3	373.2	402.3	429.7
142.5°	238.3	244.8	251.4	267.4	284.0	301.7	320.6	341.7	363.4	387.4	410.3
145°	242.9	249.4	256.0	270.9	286.3	302.3	319.4	337.7	356.0	374.9	393.2
147.5°	248.6	254.3	260.0	273.7	288.0	302.3	317.7	333.7	349.7	365.2	380.6
150°	253.1	258.2	263.4	276.6	288.6	302.3	315.4	329.7	342.9	356.0	368.0
152.5°	257.7	262.5	267.4	278.3	289.7	300.6	312.6	325.2	336.6	347.4	357.7
155°	262.9	266.9	270.9	280.6	289.7	299.4	309.2	320.6	330.3	339.4	348.0
157.5°	267.4	270.5	273.7	281.7	290.3	297.7	306.3	315.4	323.4	331.4	338.3
160°	270.9	273.8	276.6	283.4	290.3	296.6	302.9	310.3	317.7	324.0	329.7
162.5°	273.7	276.0	278.3	284.0	289.7	294.3	299.4	305.2	310.9	316.0	321.2
165°	276.0	278.0	280.0	284.6	288.6	292.0	296.0	300.6	305.2	308.6	312.6
167.5°	278.3	279.8	281.2	284.6	288.0	289.7	292.6	296.0	300.0	302.9	305.2
170°	280.0	280.6	281.2	284.0	286.3	287.4	289.2	292.0	294.9	296.6	298.9
172.5°	281.2	281.4	281.7	284.0	285.7	285.7	286.3	288.0	290.3	291.4	293.2
175°	281.7	282.0	282.3	283.4	284.6	284.0	284.0	285.2	286.3	286.9	288.0
177.5°	282.3	282.3	282.3	282.9	284.0	282.9	282.3	282.9	283.4	284.0	284.6
180°	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1739.3	1740.9	1736.1	1726.7	1725.1	1728.3	1737.7	1734.6	1726.7	1740.9	1728.3
5°	1643.2	1635.3	1632.2	1635.3	1625.9	1621.1	1630.6	1625.9	1630.6	1632.2	1636.9
7.5°	1550.2	1551.8	1542.4	1543.9	1531.3	1534.5	1534.5	1534.5	1539.2	1542.4	1548.7
10°	1469.9	1473.0	1462.0	1463.6	1454.1	1447.8	1452.6	1462.0	1462.0	1462.0	1465.2
12.5°	1405.3	1391.1	1383.2	1381.7	1370.6	1367.5	1376.9	1380.1	1388.0	1388.0	1392.7
15°	1324.9	1321.8	1315.5	1315.5	1288.7	1295.0	1298.2	1309.2	1324.9	1312.3	1315.5
17.5°	1252.5	1244.6	1236.7	1233.6	1230.4	1221.0	1233.6	1232.0	1241.5	1243.0	1247.8
20°	1187.9	1181.6	1165.8	1167.4	1170.6	1156.4	1164.3	1164.3	1173.7	1183.2	1194.2
22.5°	1124.9	1118.6	1110.7	1113.8	1104.4	1101.2	1101.2	1109.1	1120.1	1128.0	1126.4
25°	1076.0	1065.0	1060.3	1055.5	1050.8	1054.0	1049.2	1057.1	1065.0	1069.7	1065.0
27.5°	1020.9	1016.2	1006.7	1002.0	994.1	997.3	1000.4	1006.7	1011.4	1011.4	1016.2
30°	967.3	961.0	957.9	953.1	953.1	946.8	948.4	954.7	959.4	964.2	970.5
32.5°	915.3	910.6	905.9	905.9	902.7	901.2	899.6	909.0	909.0	918.5	918.5
35°	872.8	864.9	864.9	857.0	860.2	858.6	855.5	861.8	863.3	869.6	868.1
37.5°	825.5	825.5	822.4	814.5	808.2	809.8	817.7	817.7	822.4	820.8	825.5
40°	778.3	775.1	775.1	770.4	768.8	767.2	768.8	770.4	778.3	776.7	778.3
42.5°	731.0	732.6	724.7	724.7	724.7	720.0	721.6	723.1	726.3	729.4	734.2
45°	685.3	682.2	680.6	677.4	674.3	675.9	674.3	680.6	679.0	682.2	686.9
47.5°	636.5	631.8	630.2	623.9	623.9	627.0	625.5	630.2	631.8	636.5	633.3
50°	589.2	582.9	578.2	579.8	570.3	573.5	573.5	578.2	582.9	584.5	587.6
52.5°	534.1	532.5	530.9	523.0	521.5	519.9	521.5	523.0	529.3	534.1	535.7
55°	480.5	478.9	469.5	466.3	461.6	461.6	464.8	466.3	477.4	478.9	485.2
57.5°	431.7	426.9	415.9	414.3	414.3	414.3	409.6	415.9	419.1	426.9	426.9
60°	378.1	378.1	368.7	368.7	370.2	368.7	368.7	370.2	370.2	376.5	379.7
62.5°	335.6	334.0	334.0	330.8	329.3	330.8	329.3	329.3	330.8	335.6	340.3
65°	297.8	296.2	294.6	293.0	289.9	289.9	291.5	294.6	294.6	297.8	299.3
67.5°	261.5	261.5	258.4	258.4	256.8	255.2	256.8	255.2	261.5	261.5	263.1
70°	225.3	223.7	219.0	217.4	212.7	214.3	214.3	219.0	220.6	223.7	226.9
72.5°	181.2	181.2	178.0	174.9	176.4	173.3	173.3	174.9	174.9	179.6	181.2
75°	149.7	146.5	144.9	146.5	144.9	148.1	144.9	144.9	148.1	148.1	148.1
77.5°	122.9	122.9	121.3	121.3	122.9	121.3	122.9	122.9	122.9	121.3	122.9
80°	100.8	99.3	99.3	99.3	97.7	97.7	97.7	97.7	97.7	97.7	97.7
82.5°	75.6	75.6	74.0	75.6	75.6	74.0	75.6	74.0	74.0	75.6	75.6
85°	50.4	53.6	50.4	50.4	52.0	52.0	53.6	52.0	53.6	50.4	52.0
87.5°	26.8	28.4	28.4	26.8	26.8	28.4	28.4	28.4	29.9	26.8	28.4
90°	16.0	16.6	16.0	16.6	17.1	16.6	17.1	16.6	16.0	16.6	16.0
92.5°	36.3	34.3	33.1	30.9	31.4	30.3	31.4	30.9	33.1	34.3	36.3
95°	98.8	88.6	77.7	72.6	68.6	66.3	68.6	72.6	77.7	88.6	98.8
97.5°	248.6	216.0	177.7	156.0	142.3	136.0	142.3	156.0	177.7	216.0	248.6
100°	520.0	479.4	421.7	380.0	357.7	358.3	357.7	380.0	421.7	479.4	520.0
102.5°	696.3	674.3	632.6	601.7	584.0	567.4	584.0	601.7	632.6	674.3	696.3
105°	803.4	796.0	769.7	748.0	729.7	726.9	729.7	748.0	769.7	796.0	803.4
107.5°	850.6	858.3	854.9	844.6	837.2	830.9	837.2	844.6	854.9	858.3	850.6
110°	852.0	872.0	888.0	892.6	891.5	890.3	891.5	892.6	888.0	872.0	852.0

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	819.8	846.9	879.5	896.0	901.7	902.3	901.7	896.0	879.5	846.9	819.8
115°	770.6	801.7	844.6	869.7	881.2	884.0	881.2	869.7	844.6	801.7	770.6
117.5°	718.0	750.3	794.9	822.9	840.0	844.0	840.0	822.9	794.9	750.3	718.0
120°	668.3	697.2	742.3	774.3	788.0	791.4	788.0	774.3	742.3	697.2	668.3
122.5°	629.2	655.4	694.3	722.3	737.7	742.3	737.7	722.3	694.3	655.4	629.2
125°	594.3	617.2	653.7	678.9	693.2	697.2	693.2	678.9	653.7	617.2	594.3
127.5°	565.8	586.9	620.0	641.7	654.9	658.3	654.9	641.7	620.0	586.9	565.8
130°	539.4	558.9	589.2	609.7	621.7	626.3	621.7	609.7	589.2	558.9	539.4
132.5°	514.9	533.2	561.2	581.7	592.0	594.9	592.0	581.7	561.2	533.2	514.9
135°	489.4	505.7	533.7	550.9	561.2	565.2	561.2	550.9	533.7	505.7	489.4
137.5°	465.4	480.0	504.0	521.7	530.3	533.7	530.3	521.7	504.0	480.0	465.4
140°	442.0	454.3	476.0	492.0	501.2	500.6	501.2	492.0	476.0	454.3	442.0
142.5°	420.6	430.9	448.6	462.3	470.3	469.7	470.3	462.3	448.6	430.9	420.6
145°	401.4	409.7	424.0	436.0	440.6	441.7	440.6	436.0	424.0	409.7	401.4
147.5°	386.6	392.6	404.0	412.6	417.2	417.7	417.2	412.6	404.0	392.6	386.6
150°	373.4	378.9	387.4	393.7	397.2	397.2	397.2	393.7	387.4	378.9	373.4
152.5°	362.0	366.3	372.6	378.3	380.0	380.0	380.0	378.3	372.6	366.3	362.0
155°	351.4	354.9	360.0	364.6	365.7	366.3	365.7	364.6	360.0	354.9	351.4
157.5°	341.2	344.0	348.6	352.0	353.2	353.2	353.2	352.0	348.6	344.0	341.2
160°	331.7	333.7	337.7	341.2	341.2	340.6	341.2	341.2	337.7	333.7	331.7
162.5°	322.9	324.6	326.9	329.7	329.7	329.2	329.7	329.7	326.9	324.6	322.9
165°	314.0	315.4	317.7	320.0	319.4	319.4	319.4	320.0	317.7	315.4	314.0
167.5°	306.3	307.4	308.6	310.3	309.7	309.7	309.7	310.3	308.6	307.4	306.3
170°	299.4	300.0	300.6	301.7	301.2	301.2	301.2	301.7	300.6	300.0	299.4
172.5°	293.4	293.7	293.7	294.9	293.7	293.2	293.7	294.9	293.7	293.7	293.4
175°	288.0	288.0	288.0	288.6	288.0	287.4	288.0	288.6	288.0	288.0	288.0
177.5°	284.6	284.6	284.0	284.6	283.4	283.4	283.4	284.6	284.0	284.6	284.6
180°	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1	1840.1
2.5°	1740.9	1747.2	1740.9	1728.3	1740.9	1748.7	1756.6	1769.2	1775.5	1775.5	1785.0
5°	1641.6	1654.2	1649.5	1646.3	1658.9	1666.8	1679.4	1695.2	1712.5	1723.5	1736.1
7.5°	1553.4	1561.3	1569.1	1569.1	1581.7	1599.1	1618.0	1636.9	1658.9	1674.7	1684.2
10°	1476.2	1482.5	1487.2	1493.5	1512.4	1531.3	1556.5	1580.2	1599.1	1616.4	1632.2
12.5°	1402.1	1411.6	1422.6	1427.4	1441.5	1465.2	1488.8	1517.2	1547.1	1564.4	1580.2
15°	1331.3	1336.0	1348.6	1362.8	1375.4	1400.6	1430.5	1460.4	1485.6	1512.4	1526.6
17.5°	1258.8	1260.4	1293.4	1285.6	1326.5	1350.2	1365.9	1394.3	1435.2	1457.3	1479.3
20°	1187.9	1203.6	1217.8	1225.7	1247.8	1274.5	1320.2	1342.3	1375.4	1395.8	1414.7
22.5°	1132.7	1156.4	1156.4	1175.3	1186.3	1211.5	1244.6	1287.1	1323.4	1337.6	1364.3
25°	1083.9	1094.9	1113.8	1120.1	1140.6	1162.7	1184.7	1230.4	1269.8	1288.7	1307.6
27.5°	1020.9	1035.1	1060.3	1060.3	1087.1	1110.7	1137.5	1167.4	1206.8	1233.6	1254.1
30°	972.0	986.2	997.3	1014.6	1025.6	1047.7	1094.9	1117.0	1151.7	1175.3	1200.5
32.5°	926.4	937.4	946.8	965.7	978.4	1003.6	1028.8	1068.2	1098.1	1120.1	1146.9
35°	875.9	887.0	899.6	913.8	932.7	956.3	979.9	1013.0	1042.9	1063.4	1085.5
37.5°	828.7	836.6	855.5	864.9	880.7	902.7	932.7	967.3	994.1	1009.9	1031.9
40°	783.0	789.3	803.5	820.8	831.8	849.2	880.7	910.6	943.7	962.6	979.9
42.5°	734.2	742.0	754.6	772.0	789.3	808.2	825.5	860.2	890.1	905.9	924.8
45°	691.6	696.3	705.8	723.1	740.5	754.6	781.4	812.9	841.3	853.9	874.4
47.5°	641.2	645.9	660.1	668.0	686.9	705.8	732.6	764.1	789.3	801.9	820.8
50°	589.2	593.9	603.4	620.7	633.3	653.8	677.4	704.2	735.7	753.1	764.1
52.5°	538.8	548.3	556.1	570.3	586.1	606.5	628.6	653.8	680.6	697.9	710.5
55°	488.4	496.3	505.7	513.6	532.5	551.4	576.6	600.2	623.9	639.6	653.8
57.5°	431.7	442.7	452.2	467.9	482.1	497.8	526.2	545.1	573.5	584.5	597.1
60°	382.8	393.9	401.7	414.3	426.9	447.4	466.3	490.0	513.6	527.8	543.5
62.5°	341.9	346.6	351.3	363.9	376.5	395.4	414.3	438.0	463.2	471.1	483.7
65°	300.9	305.6	313.5	324.5	334.0	345.0	365.5	384.4	408.0	420.6	425.4
67.5°	266.3	271.0	272.6	280.4	288.3	300.9	311.9	330.8	352.9	360.8	370.2
70°	226.9	234.7	236.3	242.6	245.8	253.6	266.3	280.4	297.8	311.9	319.8
72.5°	181.2	192.2	195.4	204.8	209.5	217.4	226.9	237.9	248.9	255.2	261.5
75°	148.1	151.2	152.8	160.7	168.6	179.6	184.3	190.6	200.1	208.0	214.3
77.5°	122.9	124.5	126.0	126.0	127.6	133.9	143.4	151.2	157.5	160.7	165.4
80°	99.3	97.7	97.7	99.3	99.3	99.3	102.4	113.4	116.6	124.5	122.9
82.5°	77.2	74.0	75.6	74.0	74.0	74.0	74.0	75.6	75.6	80.3	83.5
85°	50.4	52.0	50.4	50.4	48.8	50.4	48.8	48.8	47.3	47.3	45.7
87.5°	26.8	28.4	26.8	26.8	25.2	26.8	25.2	25.2	23.6	23.6	20.5
90°	15.4	14.9	14.3	13.7	14.3	12.6	10.9	9.1	7.4	6.8	6.3
92.5°	38.3	44.0	56.6	79.4	106.3	117.7	88.0	57.7	39.4	34.2	29.1
95°	109.1	139.4	205.7	274.9	338.9	301.7	208.0	122.9	74.3	63.2	52.0
97.5°	281.2	356.6	472.6	538.9	521.2	389.2	231.4	132.6	84.6	72.3	60.0
100°	560.6	627.4	673.7	653.7	541.2	365.7	215.4	130.9	90.9	79.8	68.6
102.5°	718.3	750.3	740.6	659.4	504.0	331.4	201.7	133.1	98.3	88.3	78.3
105°	810.9	800.0	742.9	623.4	459.4	304.6	196.6	137.7	106.9	98.0	89.1
107.5°	842.9	798.3	708.6	572.0	420.0	285.2	195.4	145.1	117.7	109.4	101.1
110°	832.0	760.0	654.9	524.0	387.4	274.9	198.3	154.9	129.1	121.1	113.1

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	792.6	709.7	601.7	482.3	365.7	269.1	204.0	164.6	141.1	133.4	125.7
115°	739.4	655.4	556.0	450.3	351.4	268.6	210.3	175.4	153.7	146.0	138.3
117.5°	685.7	608.6	520.6	429.2	341.7	269.1	218.3	186.9	165.1	158.0	150.9
120°	639.4	570.9	493.7	413.2	335.4	271.4	227.4	197.7	177.1	170.0	162.9
122.5°	602.9	540.6	472.6	400.0	331.4	275.4	236.0	209.1	189.1	181.4	173.7
125°	571.4	516.6	454.3	389.2	328.0	279.4	245.1	220.0	200.0	192.3	184.6
127.5°	544.6	494.3	437.7	378.9	326.3	284.0	252.6	229.7	210.3	202.6	194.9
130°	520.0	473.7	422.3	370.9	324.6	288.6	260.0	238.3	219.4	211.7	204.0
132.5°	496.6	454.3	408.0	363.4	324.0	292.0	266.9	245.7	227.4	220.0	212.6
135°	473.2	436.0	395.4	357.2	323.4	295.4	272.6	253.1	235.4	227.7	220.0
137.5°	450.9	417.7	383.4	351.4	322.3	297.7	277.2	258.3	241.1	234.0	226.9
140°	429.7	402.3	373.2	346.3	321.7	300.0	280.6	263.4	246.9	239.8	232.6
142.5°	410.3	387.4	363.4	341.7	320.6	301.7	284.0	267.4	251.4	244.8	238.3
145°	393.2	374.9	356.0	337.7	319.4	302.3	286.3	270.9	256.0	249.4	242.9
147.5°	380.6	365.2	349.7	333.7	317.7	302.3	288.0	273.7	260.0	254.3	248.6
150°	368.0	356.0	342.9	329.7	315.4	302.3	288.6	276.6	263.4	258.2	253.1
152.5°	357.7	347.4	336.6	325.2	312.6	300.6	289.7	278.3	267.4	262.5	257.7
155°	348.0	339.4	330.3	320.6	309.2	299.4	289.7	280.6	270.9	266.9	262.9
157.5°	338.3	331.4	323.4	315.4	306.3	297.7	290.3	281.7	273.7	270.5	267.4
160°	329.7	324.0	317.7	310.3	302.9	296.6	290.3	283.4	276.6	273.8	270.9
162.5°	321.2	316.0	310.9	305.2	299.4	294.3	289.7	284.0	278.3	276.0	273.7
165°	312.6	308.6	305.2	300.6	296.0	292.0	288.6	284.6	280.0	278.0	276.0
167.5°	305.2	302.9	300.0	296.0	292.6	289.7	288.0	284.6	281.2	279.8	278.3
170°	298.9	296.6	294.9	292.0	289.2	287.4	286.3	284.0	281.2	280.6	280.0
172.5°	293.2	291.4	290.3	288.0	286.3	285.7	285.7	284.0	281.7	281.4	281.2
175°	288.0	286.9	286.3	285.2	284.0	284.0	284.6	283.4	282.3	282.0	281.7
177.5°	284.6	284.0	283.4	282.9	282.3	282.9	284.0	282.9	282.3	282.3	282.3
180°	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1840.1	1840.1	1840.1	1840.1
2.5°	1792.9	1803.9	1825.9	1844.8
5°	1755.0	1772.4	1805.5	1838.5
7.5°	1709.4	1736.1	1778.7	1824.4
10°	1665.2	1699.9	1751.9	1805.5
12.5°	1621.1	1657.4	1712.5	1781.8
15°	1569.1	1607.0	1673.1	1756.6
17.5°	1523.5	1573.9	1633.7	1717.2
20°	1474.6	1512.4	1589.6	1677.8
22.5°	1413.2	1476.2	1548.7	1641.6
25°	1364.3	1419.5	1491.9	1597.5
27.5°	1304.5	1369.1	1457.3	1550.2
30°	1255.6	1309.2	1391.1	1503.0
32.5°	1198.9	1261.9	1347.0	1457.3
35°	1148.5	1202.1	1282.4	1394.3
37.5°	1088.6	1146.9	1236.7	1336.0
40°	1036.6	1093.4	1178.4	1271.4
42.5°	973.6	1033.5	1118.6	1197.3
45°	923.2	978.4	1046.1	1118.6
47.5°	861.8	920.1	986.2	1036.6
50°	806.6	860.2	912.2	954.7
52.5°	746.8	795.6	842.9	874.4
55°	691.6	729.4	767.2	789.3
57.5°	627.0	663.3	694.8	707.4
60°	570.3	600.2	620.7	634.9
62.5°	510.4	532.5	548.3	556.1
65°	452.2	467.9	475.8	483.7
67.5°	392.3	406.5	411.2	420.6
70°	329.3	345.0	348.2	352.9
72.5°	282.0	282.0	288.3	294.6
75°	225.3	228.4	231.6	231.6
77.5°	176.4	176.4	179.6	181.2
80°	129.2	130.8	130.8	129.2
82.5°	88.2	91.4	88.2	86.6
85°	48.8	55.1	52.0	52.0
87.5°	20.5	20.5	23.6	20.5
90°	5.1	3.4	2.3	1.1
92.5°	23.4	18.3	12.6	8.6
95°	37.1	27.4	21.1	19.4
97.5°	45.1	36.6	31.4	30.9
100°	54.9	46.9	42.9	42.3
102.5°	66.3	58.9	55.4	54.3
105°	78.3	71.4	68.0	66.3
107.5°	90.9	84.0	80.6	78.9
110°	103.4	97.1	94.3	92.6

TEST NUMBER: P1012356

CATALOG NUMBER: S123RDIP-B1165D585UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	116.0	109.7	106.9	105.1
115°	128.6	122.9	119.4	117.1
117.5°	140.0	134.9	132.0	129.1
120°	152.0	146.3	143.4	141.7
122.5°	163.4	157.1	154.3	152.6
125°	173.7	167.4	164.0	162.9
127.5°	182.9	176.6	172.6	170.9
130°	192.0	185.1	180.0	178.3
132.5°	200.6	192.0	186.3	184.0
135°	208.0	199.4	193.1	190.9
137.5°	214.9	205.7	199.4	197.1
140°	221.1	212.0	206.3	203.4
142.5°	226.9	218.9	212.6	210.3
145°	233.1	224.6	219.4	217.7
147.5°	238.9	231.4	226.3	225.1
150°	245.1	237.7	233.1	232.6
152.5°	250.9	244.6	240.0	240.0
155°	256.6	250.9	247.4	247.4
157.5°	261.7	256.6	253.7	253.1
160°	266.9	262.3	260.0	260.0
162.5°	270.3	266.9	265.1	265.1
165°	273.7	270.9	269.7	270.3
167.5°	276.6	274.3	273.7	274.3
170°	278.9	277.2	276.6	277.7
172.5°	280.6	279.4	279.4	280.0
175°	281.7	280.6	281.2	281.7
177.5°	282.3	281.7	282.3	282.9
180°	282.3	282.3	282.3	282.3

(END OF REPORT)