

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012414

Luminaire Tested: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012414
REPORT IS A COMBINATION OF REPORTS P993137 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4994.0 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	26		
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23		
2	85	78	72	67	75	70	65	61	55	51	49	41	38	37	28	26	25	20		
3	77	69	62	56	69	62	56	51	48	44	41	36	34	31	25	23	22	17		
4	71	61	53	48	63	55	48	43	43	39	35	32	29	27	22	21	19	15		
5	65	54	47	41	58	49	42	37	39	34	30	29	26	24	20	18	17	13		
6	60	49	41	35	53	44	37	32	35	30	26	26	23	21	18	16	15	12		
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	10		
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	15	13	12	9		
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11	9		
10	44	33	26	22	40	30	24	20	24	20	16	18	15	13	13	11	10	8		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5702	5702	5702	5702
5°	5707	6567	5721	4872
10°	5655	7927	5680	4255
15°	5598	8997	5598	3752
20°	5483	9704	5513	3329
25°	5399	9220	5389	3037
30°	5302	6389	5289	2753
35°	5184	4101	5159	2538
40°	5037	2896	5012	2324
45°	4782	2318	4775	2116
50°	4469	1939	4454	1872
55°	4117	1598	4084	1587
60°	3772	1321	3735	1349
65°	3365	1057	3387	1143
70°	2992	735	3072	925
75°	2537	546	2640	711
80°	2020	360	2193	533
85°	1441	171	1566	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7612 cd/sqm

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.0	1.0
10°-20°	162.8	3.3
20°-30°	256.5	5.1
30°-40°	266.7	5.3
40°-50°	228.2	4.6
50°-60°	173.9	3.5
60°-70°	111.4	2.2
70°-80°	53.4	1.1
80°-90°	16.7	0.3
90°-100°	264.9	5.3
100°-110°	775.6	15.5
110°-120°	757.4	15.2
120°-130°	603.2	12.1
130°-140°	475.9	9.5
140°-150°	355.0	7.1
150°-160°	247.5	5.0
160°-170°	145.4	2.9
170°-180°	47.3	0.9
0°-30°	471.3	9.4
0°-40°	738.0	14.8
0°-60°	1140.1	22.8
0°-90°	1321.7	26.5
90°-120°	1797.9	36.0
90°-150°	3232.0	64.7
90°-180°	3672.0	73.5
0°-180°	4994.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	530	530	530	530	530	
5°	529	629	531	467	529	50
15°	506	894	506	373	506	142
25°	460	921	459	303	460	212
35°	401	400	400	247	401	251
45°	322	213	322	195	322	248
55°	227	134	225	133	227	204
65°	139	77	140	83	139	139
75°	67	33	69	43	67	72
85°	15	8	16	15	15	17
90°	2	29	2	29	2	3
95°	34	115	34	115	34	36
105°	115	1257	115	1257	115	122
115°	203	1529	203	1529	203	201
125°	282	1206	282	1206	282	250
135°	330	977	330	977	330	255
145°	376	764	376	764	376	236
155°	428	634	428	634	428	197
165°	467	552	467	552	467	132
175°	487	497	487	497	487	46
180°	488	488	488	488	488	

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	531.1	534.7	537.4	539.2	543.8	546.5	548.8	552.8	552.8	553.7	555.6
5°	529.3	537.0	542.4	549.7	559.2	563.7	570.1	575.5	583.2	587.3	591.4
7.5°	525.2	536.1	547.4	558.3	572.3	581.4	587.8	601.8	611.8	624.0	633.6
10°	519.7	534.7	549.2	566.0	585.0	598.6	608.2	626.8	645.8	663.0	677.6
12.5°	512.9	531.1	551.9	572.3	599.1	612.7	628.1	651.2	678.5	700.2	719.7
15°	505.7	526.5	550.1	575.1	608.6	627.7	649.9	678.0	708.4	739.7	766.4
17.5°	494.3	520.6	546.9	583.2	622.7	634.0	653.1	691.6	729.3	757.4	790.0
20°	483.0	512.5	545.6	578.2	620.9	647.2	664.9	705.7	746.0	780.0	811.3
22.5°	472.6	503.4	537.9	579.1	619.0	645.4	667.6	710.2	756.9	795.0	833.6
25°	459.9	493.4	531.5	570.5	619.0	639.0	663.5	712.9	762.4	806.4	854.0
27.5°	446.3	480.3	517.9	557.8	602.3	631.7	655.8	708.8	769.2	816.3	865.3
30°	432.7	467.6	503.9	539.7	589.6	617.7	645.4	703.9	772.8	826.8	864.4
32.5°	419.5	449.0	484.8	519.7	569.2	600.0	631.3	698.9	774.2	819.5	837.6
35°	401.4	432.2	461.2	498.4	548.3	578.7	615.4	698.4	768.3	796.4	787.3
37.5°	384.6	410.4	438.1	471.2	522.5	561.9	600.0	686.6	748.8	750.6	699.3
40°	366.0	387.3	410.4	445.4	500.7	539.7	581.0	668.5	713.4	686.6	596.4
42.5°	344.7	363.7	381.9	415.9	476.2	519.7	564.2	645.8	662.1	600.5	506.6
45°	322.0	337.4	354.2	390.0	450.3	493.4	537.9	610.9	594.1	507.0	417.7
47.5°	298.4	311.6	327.9	360.5	422.7	466.7	508.8	561.0	518.4	424.9	350.1
50°	274.8	285.3	301.1	334.7	394.6	434.5	473.5	507.5	447.6	364.6	289.3
52.5°	251.7	259.9	276.2	304.8	362.8	400.9	429.0	442.2	381.4	301.1	251.2
55°	227.2	236.3	247.2	276.2	333.8	361.9	380.5	380.0	317.5	255.3	207.7
57.5°	203.6	211.8	221.3	250.3	297.1	316.1	332.0	324.3	264.9	209.1	178.2
60°	182.8	187.3	197.7	222.2	257.6	273.9	283.0	269.8	216.3	176.4	147.4
62.5°	160.1	164.6	173.2	196.4	218.1	226.8	234.5	217.7	178.7	143.8	126.1
65°	139.2	145.1	150.6	169.2	181.0	191.4	190.5	176.4	139.7	117.0	102.5
67.5°	121.1	123.4	127.9	139.2	144.7	152.4	152.8	137.0	112.5	95.2	86.6
70°	101.6	103.9	107.0	112.5	116.1	117.9	117.0	102.9	84.8	74.4	66.7
72.5°	84.8	84.4	86.6	86.6	90.2	89.8	87.1	76.2	64.4	55.8	51.2
75°	66.7	67.1	67.6	66.7	65.3	63.5	61.2	53.1	45.4	41.3	37.2
77.5°	52.2	51.2	51.7	48.5	46.7	44.9	41.7	37.6	31.3	30.4	28.6
80°	37.2	36.7	36.3	34.9	30.8	29.0	26.8	24.5	23.1	22.2	21.8
82.5°	24.9	24.9	24.0	21.3	19.0	17.7	17.2	16.3	15.0	15.0	14.5
85°	15.0	14.5	13.6	10.9	9.5	9.5	9.5	9.5	8.6	8.6	8.2
87.5°	5.9	5.4	4.1	4.1	3.6	3.6	3.6	3.2	3.2	2.7	2.7
90°	2.0	4.0	5.9	8.9	10.9	11.9	12.8	15.8	18.8	21.7	24.7
92.5°	14.8	21.7	31.6	40.5	50.4	59.3	68.2	99.8	152.2	203.6	183.8
95°	33.6	36.6	47.4	64.2	89.9	109.2	128.5	212.5	359.7	521.8	586.0
97.5°	53.4	54.4	63.2	78.1	103.8	125.0	146.3	229.3	400.2	673.0	901.3
100°	73.1	74.1	81.0	94.9	118.6	137.8	157.1	226.3	372.6	632.5	935.9
102.5°	93.9	95.9	101.8	114.6	135.4	152.7	170.0	230.3	348.9	573.2	871.6
105°	114.6	117.6	123.5	135.4	154.2	169.5	184.8	238.2	340.0	526.7	794.6
107.5°	136.4	139.3	145.3	157.1	174.9	189.2	203.6	251.0	338.0	493.1	726.4
110°	160.1	163.1	168.0	178.9	195.7	209.5	223.3	267.8	342.9	475.4	670.0

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	181.8	184.8	189.7	200.6	217.4	230.8	244.1	284.6	352.8	465.5	632.5
115°	202.6	206.5	212.5	222.4	239.2	252.5	265.8	303.4	363.7	464.5	607.8
117.5°	223.3	228.3	233.2	242.1	260.9	273.2	285.6	323.2	377.5	465.5	591.0
120°	245.1	248.1	253.0	262.9	281.7	294.0	306.4	341.9	393.3	469.4	580.1
122.5°	263.9	266.8	271.8	282.6	300.4	313.8	327.1	361.7	408.2	476.3	573.2
125°	281.7	283.6	289.6	300.4	319.2	332.5	345.9	380.5	424.0	483.3	567.3
127.5°	295.5	298.5	305.4	316.2	337.0	350.4	363.7	397.3	436.8	491.2	564.3
130°	308.3	311.3	320.2	332.1	352.8	366.2	379.5	412.1	449.7	499.1	561.3
132.5°	318.2	322.2	332.1	346.9	367.6	380.5	393.3	425.0	461.5	505.0	560.3
135°	330.1	334.0	344.9	359.7	380.5	393.8	407.2	437.8	471.4	510.9	559.4
137.5°	341.0	344.9	355.8	371.6	392.3	404.6	417.0	446.7	479.3	514.9	557.4
140°	351.8	356.8	366.6	382.5	402.2	414.6	426.9	455.6	485.2	518.8	556.4
142.5°	363.7	367.6	378.5	392.3	412.1	423.4	434.8	462.5	491.2	521.8	554.4
145°	376.5	379.5	388.4	403.2	420.0	431.4	442.7	468.4	495.1	522.8	552.4
147.5°	389.4	391.4	400.2	413.1	429.9	439.8	449.7	473.4	498.1	522.8	549.5
150°	402.2	403.2	411.1	424.0	437.8	446.7	455.6	478.3	499.1	522.8	545.5
152.5°	415.1	415.1	423.0	433.8	445.7	454.1	462.5	481.3	501.0	519.8	540.6
155°	427.9	427.9	433.8	443.7	454.6	461.5	468.4	485.2	501.0	517.8	534.6
157.5°	437.8	438.8	443.7	452.6	462.5	468.0	473.4	487.2	502.0	514.9	529.7
160°	449.7	449.7	453.6	461.5	468.4	473.4	478.3	490.2	502.0	512.9	523.8
162.5°	458.6	458.6	461.5	467.4	473.4	477.4	481.3	491.2	501.0	509.0	517.8
165°	467.4	466.5	468.4	473.4	477.3	480.8	484.2	492.2	499.1	505.0	511.9
167.5°	474.4	473.4	474.4	478.3	481.3	483.8	486.2	492.2	498.1	501.0	506.0
170°	480.3	478.3	479.3	482.3	484.2	485.2	486.2	491.2	495.1	497.1	500.1
172.5°	484.2	483.3	483.3	485.2	486.2	486.7	487.2	491.2	494.1	494.1	495.1
175°	487.2	486.2	485.2	487.2	487.2	487.7	488.2	490.2	492.2	491.2	491.2
177.5°	489.2	488.2	487.2	488.2	488.2	488.2	488.2	489.2	491.2	489.2	488.2
180°	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	559.2	559.2	563.3	567.3	565.1	566.4	571.4	569.6	573.2	572.8	574.2
5°	601.4	606.4	610.4	619.0	620.4	619.0	627.7	629.9	634.0	629.0	631.3
7.5°	649.0	659.4	669.4	682.1	686.2	687.1	691.6	698.0	703.4	693.4	698.4
10°	695.2	711.1	731.5	742.9	752.8	756.5	760.1	764.2	770.5	776.4	771.9
12.5°	745.1	768.3	787.8	808.2	820.4	819.1	829.5	832.2	837.2	838.6	840.4
15°	785.9	818.6	830.8	861.2	863.9	873.0	884.8	895.2	896.6	893.9	893.9
17.5°	824.9	853.1	874.8	899.3	904.3	912.0	927.0	932.0	933.8	933.3	933.3
20°	856.7	875.3	912.0	932.4	940.6	950.6	961.0	967.4	968.7	970.5	967.8
22.5°	877.6	905.7	935.6	952.4	959.2	962.8	969.6	971.4	969.2	969.6	970.1
25°	893.9	921.5	939.7	944.2	943.8	939.2	934.2	925.6	924.7	921.1	913.8
27.5°	898.4	908.8	906.6	888.0	869.4	867.6	837.6	821.3	802.7	805.4	795.0
30°	873.9	860.3	828.1	781.0	761.5	729.7	696.1	661.2	647.6	632.7	660.3
32.5°	814.1	765.5	708.4	647.2	614.5	586.4	550.6	525.2	510.7	498.4	522.0
35°	723.8	648.1	572.3	514.3	487.5	462.1	428.6	415.9	397.7	399.5	401.8
37.5°	607.7	524.3	467.1	410.0	392.3	381.9	357.4	337.9	331.5	329.7	329.7
40°	498.9	430.4	379.6	334.7	321.1	312.5	293.0	283.9	277.1	275.3	277.6
42.5°	412.7	354.2	314.7	284.8	275.3	264.4	256.2	244.9	243.5	240.4	244.4
45°	346.5	295.7	266.2	244.4	236.3	232.2	223.1	216.3	213.6	213.2	216.3
47.5°	293.9	254.4	228.6	215.0	208.6	204.5	196.8	194.1	191.4	192.3	190.9
50°	246.7	217.2	200.5	188.2	184.1	180.0	175.1	172.3	171.0	171.0	170.5
52.5°	211.8	187.3	176.4	165.1	163.3	161.0	155.6	153.7	151.5	151.0	152.8
55°	181.4	164.6	153.7	146.9	145.1	140.6	138.3	136.1	134.7	133.8	134.2
57.5°	155.1	142.4	135.1	129.3	126.1	124.3	120.2	119.7	118.8	118.8	118.4
60°	133.3	124.3	115.6	112.0	109.8	107.5	107.0	104.3	102.9	103.9	103.4
62.5°	112.9	105.7	100.7	96.6	95.2	93.4	92.1	91.2	89.8	90.2	90.2
65°	94.3	88.4	84.8	81.2	80.7	78.9	78.5	77.6	77.6	77.1	78.0
67.5°	77.6	73.5	70.3	68.0	66.7	67.1	65.3	63.9	63.9	63.5	64.9
70°	61.7	59.4	56.2	53.5	51.7	51.7	49.4	49.0	49.0	49.0	48.5
72.5°	47.6	43.5	42.2	41.3	41.3	41.3	40.4	40.4	39.9	40.4	39.9
75°	35.4	34.9	34.0	33.6	33.6	33.1	32.7	32.7	32.7	32.7	32.7
77.5°	27.7	27.7	26.8	26.3	26.3	26.3	25.9	25.9	25.4	25.4	25.4
80°	20.4	20.4	19.5	19.5	19.5	19.0	19.0	19.0	19.5	19.0	19.0
82.5°	14.1	14.1	13.6	14.1	13.6	13.2	13.2	13.2	12.7	13.2	13.2
85°	8.2	8.2	7.7	7.3	7.7	7.7	7.3	7.7	7.3	7.7	7.3
87.5°	3.2	2.7	2.7	2.7	2.3	2.7	2.3	2.3	2.7	2.3	2.7
90°	23.7	24.7	25.7	26.7	27.7	28.7	27.7	28.7	29.6	28.7	29.6
92.5°	137.4	97.8	76.1	66.2	62.8	59.3	57.3	53.4	54.4	52.4	54.4
95°	475.4	355.8	241.1	188.8	171.0	153.2	134.4	125.5	118.6	114.6	118.6
97.5°	931.9	817.3	616.7	486.2	429.9	373.6	307.3	269.8	246.1	235.2	246.1
100°	1130.6	1165.2	1085.1	969.5	899.4	829.2	729.3	657.2	618.7	619.6	618.7
102.5°	1140.5	1280.8	1297.6	1242.2	1204.2	1166.1	1094.0	1040.6	1010.0	981.3	1010.0
105°	1078.2	1284.7	1383.6	1402.3	1389.4	1376.6	1331.2	1293.6	1262.0	1257.1	1262.0
107.5°	989.2	1225.4	1380.6	1457.7	1471.1	1484.4	1478.4	1460.6	1447.8	1436.9	1447.8
110°	906.2	1132.5	1314.4	1438.9	1473.5	1508.1	1535.8	1543.7	1541.7	1539.7	1541.7

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	834.1	1040.6	1227.4	1370.7	1417.6	1464.6	1520.9	1549.6	1559.5	1560.5	1559.5
115°	778.7	961.6	1133.5	1278.8	1332.6	1386.5	1460.6	1504.1	1523.9	1528.8	1523.9
117.5°	742.2	900.3	1052.5	1185.9	1241.8	1297.6	1374.7	1423.1	1452.7	1459.7	1452.7
120°	714.5	853.9	987.3	1105.9	1155.8	1205.7	1283.8	1339.1	1362.8	1368.7	1362.8
122.5°	691.8	817.3	934.9	1042.6	1088.0	1133.5	1200.7	1249.2	1275.8	1283.8	1275.8
125°	673.0	785.7	893.4	988.3	1027.8	1067.3	1130.6	1174.1	1198.8	1205.7	1198.8
127.5°	655.2	757.0	854.8	941.8	978.4	1014.9	1072.3	1109.8	1132.5	1138.5	1132.5
130°	641.4	730.3	819.3	899.3	932.9	966.5	1018.9	1054.5	1075.2	1083.1	1075.2
132.5°	628.5	705.6	785.7	858.8	890.4	922.0	970.5	1006.0	1023.8	1028.8	1023.8
135°	617.7	683.9	754.0	818.3	846.4	874.6	923.0	952.7	970.5	977.4	970.5
137.5°	607.8	663.1	722.4	779.7	804.9	830.1	871.6	902.3	917.1	923.0	917.1
140°	598.9	645.3	695.7	743.2	764.4	785.7	823.2	850.9	866.7	865.7	866.7
142.5°	591.0	628.5	670.0	709.6	727.4	745.1	775.8	799.5	813.3	812.4	813.3
145°	584.1	615.7	648.3	679.9	694.2	708.6	733.3	754.0	761.9	763.9	761.9
147.5°	577.1	604.8	631.5	658.2	668.6	678.9	698.7	713.5	721.4	722.4	721.4
150°	570.2	593.0	615.7	636.4	645.8	655.2	670.0	680.9	686.8	686.8	686.8
152.5°	562.3	582.1	600.9	618.7	626.1	633.5	644.3	654.2	657.2	657.2	657.2
155°	554.4	571.2	587.0	601.9	607.8	613.7	622.6	630.5	632.5	633.5	632.5
157.5°	545.5	559.4	573.2	585.1	590.0	594.9	602.8	608.8	610.7	610.7	610.7
160°	536.6	549.5	560.3	570.2	573.7	577.1	584.1	590.0	590.0	589.0	590.0
162.5°	527.7	537.6	546.5	555.4	558.3	561.3	565.3	570.2	570.2	569.2	570.2
165°	519.8	527.7	533.7	540.6	543.0	545.5	549.5	553.4	552.4	552.4	552.4
167.5°	511.9	518.8	523.8	527.7	529.7	531.7	533.7	536.6	535.6	535.6	535.6
170°	505.0	509.9	512.9	516.9	517.8	518.8	519.8	521.8	520.8	520.8	520.8
172.5°	498.1	502.0	504.0	507.0	507.5	508.0	508.0	509.9	508.0	507.0	508.0
175°	493.1	495.1	496.1	498.1	498.1	498.1	498.1	499.1	498.1	497.1	498.1
177.5°	489.2	490.2	491.2	492.2	492.2	492.2	491.2	492.2	490.2	490.2	490.2
180°	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	571.9	569.2	567.3	566.0	564.6	568.7	563.3	557.4	553.3	550.6	549.7
5°	631.7	625.9	620.9	616.8	617.7	617.7	608.2	597.7	588.7	583.7	578.2
7.5°	701.1	694.8	684.8	682.5	680.7	669.4	659.9	640.8	629.5	618.1	608.2
10°	770.1	761.9	752.4	749.2	744.7	730.6	716.1	691.6	677.6	656.7	643.5
12.5°	834.5	824.5	815.0	812.7	805.9	793.7	768.7	743.3	719.3	697.1	673.9
15°	888.4	885.7	871.2	862.1	847.2	830.4	824.9	790.5	760.1	737.0	695.2
17.5°	933.8	921.1	907.5	901.6	895.7	876.2	856.7	821.3	788.7	754.7	727.9
20°	970.1	956.0	946.5	937.9	935.2	912.9	882.1	850.8	815.0	776.9	742.0
22.5°	971.9	970.1	963.7	958.7	953.3	938.8	914.3	875.3	837.2	795.5	749.7
25°	934.2	931.5	949.7	945.1	948.8	943.3	930.2	897.5	853.1	804.1	757.8
27.5°	820.9	848.5	877.1	887.1	893.9	913.4	919.7	901.6	865.8	813.6	761.9
30°	666.7	703.4	749.7	774.6	793.7	829.9	877.1	883.0	866.2	824.5	761.0
32.5°	523.4	556.9	594.1	623.6	649.0	723.4	786.9	832.7	840.8	819.1	763.3
35°	421.8	436.3	471.7	499.8	534.2	597.7	672.6	746.5	796.4	799.1	756.5
37.5°	347.8	355.6	386.4	402.3	422.7	478.5	548.3	644.9	722.5	759.2	737.4
40°	288.0	305.7	323.4	332.4	346.9	385.5	452.6	528.3	624.5	692.5	707.9
42.5°	249.9	257.6	268.9	281.6	290.7	324.3	369.2	438.6	525.2	620.0	662.6
45°	220.4	223.1	234.9	243.1	252.6	276.2	307.9	366.0	442.2	535.6	608.2
47.5°	195.9	201.4	207.7	212.7	219.0	237.2	264.4	306.6	373.7	457.1	535.1
50°	174.2	177.3	185.5	187.8	192.3	205.0	225.9	258.1	313.4	380.0	460.8
52.5°	153.7	159.6	162.8	166.0	170.1	180.5	194.1	220.4	262.1	324.7	393.2
55°	137.9	139.7	144.2	146.9	150.1	157.4	169.2	188.7	221.3	271.2	336.1
57.5°	122.4	122.4	127.0	129.3	132.4	137.9	148.3	163.3	186.8	224.0	283.4
60°	106.1	106.6	110.2	112.9	113.8	119.3	127.9	139.7	157.8	185.0	233.6
62.5°	91.6	93.9	95.7	96.6	99.8	102.9	110.2	118.4	131.1	155.1	189.6
65°	79.4	79.8	81.2	82.1	83.4	87.1	92.5	98.0	108.8	126.5	154.6
67.5°	65.3	67.1	68.9	68.9	70.3	72.1	77.6	82.1	90.2	100.7	119.7
70°	49.0	49.9	52.6	54.0	55.8	59.0	61.7	64.4	70.7	78.5	93.0
72.5°	40.8	40.8	41.7	42.2	42.2	44.4	48.5	51.2	54.4	59.9	69.8
75°	32.7	32.7	34.0	33.6	34.5	35.4	35.8	37.6	39.5	43.5	49.4
77.5°	25.9	26.3	26.3	26.8	26.8	27.2	27.7	28.6	29.5	31.7	34.5
80°	19.0	19.5	19.5	20.0	20.0	20.4	20.9	21.3	22.2	23.1	24.5
82.5°	13.2	13.6	13.6	14.1	13.6	14.1	14.5	14.5	15.0	15.9	16.3
85°	7.7	7.7	8.2	7.7	7.7	7.7	8.2	8.2	8.6	10.0	10.0
87.5°	2.3	2.7	2.3	2.7	2.7	2.7	2.7	3.2	3.2	3.6	4.1
90°	28.7	27.7	28.7	27.7	26.7	25.7	24.7	23.7	24.7	21.7	18.8
92.5°	53.4	57.3	59.3	62.8	66.2	76.1	97.8	137.4	183.8	203.6	152.2
95°	125.5	134.4	153.2	171.0	188.8	241.1	355.8	475.4	586.0	521.8	359.7
97.5°	269.8	307.3	373.6	429.9	486.2	616.7	817.3	931.9	901.3	673.0	400.2
100°	657.2	729.3	829.2	899.4	969.5	1085.1	1165.2	1130.6	935.9	632.5	372.6
102.5°	1040.6	1094.0	1166.1	1204.2	1242.2	1297.6	1280.8	1140.5	871.6	573.2	348.9
105°	1293.6	1331.2	1376.6	1389.4	1402.3	1383.6	1284.7	1078.2	794.6	526.7	340.0
107.5°	1460.6	1478.4	1484.4	1471.1	1457.7	1380.6	1225.4	989.2	726.4	493.1	338.0
110°	1543.7	1535.8	1508.1	1473.5	1438.9	1314.4	1132.5	906.2	670.0	475.4	342.9

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1549.6	1520.9	1464.6	1417.6	1370.7	1227.4	1040.6	834.1	632.5	465.5	352.8
115°	1504.1	1460.6	1386.5	1332.6	1278.8	1133.5	961.6	778.7	607.8	464.5	363.7
117.5°	1423.1	1374.7	1297.6	1241.8	1185.9	1052.5	900.3	742.2	591.0	465.5	377.5
120°	1339.1	1283.8	1205.7	1155.8	1105.9	987.3	853.9	714.5	580.1	469.4	393.3
122.5°	1249.2	1200.7	1133.5	1088.0	1042.6	934.9	817.3	691.8	573.2	476.3	408.2
125°	1174.1	1130.6	1067.3	1027.8	988.3	893.4	785.7	673.0	567.3	483.3	424.0
127.5°	1109.8	1072.3	1014.9	978.4	941.8	854.8	757.0	655.2	564.3	491.2	436.8
130°	1054.5	1018.9	966.5	932.9	899.3	819.3	730.3	641.4	561.3	499.1	449.7
132.5°	1006.0	970.5	922.0	890.4	858.8	785.7	705.6	628.5	560.3	505.0	461.5
135°	952.7	923.0	874.6	846.4	818.3	754.0	683.9	617.7	559.4	510.9	471.4
137.5°	902.3	871.6	830.1	804.9	779.7	722.4	663.1	607.8	557.4	514.9	479.3
140°	850.9	823.2	785.7	764.4	743.2	695.7	645.3	598.9	556.4	518.8	485.2
142.5°	799.5	775.8	745.1	727.4	709.6	670.0	628.5	591.0	554.4	521.8	491.2
145°	754.0	733.3	708.6	694.2	679.9	648.3	615.7	584.1	552.4	522.8	495.1
147.5°	713.5	698.7	678.9	668.6	658.2	631.5	604.8	577.1	549.5	522.8	498.1
150°	680.9	670.0	655.2	645.8	636.4	615.7	593.0	570.2	545.5	522.8	499.1
152.5°	654.2	644.3	633.5	626.1	618.7	600.9	582.1	562.3	540.6	519.8	501.0
155°	630.5	622.6	613.7	607.8	601.9	587.0	571.2	554.4	534.6	517.8	501.0
157.5°	608.8	602.8	594.9	590.0	585.1	573.2	559.4	545.5	529.7	514.9	502.0
160°	590.0	584.1	577.1	573.7	570.2	560.3	549.5	536.6	523.8	512.9	502.0
162.5°	570.2	565.3	561.3	558.3	555.4	546.5	537.6	527.7	517.8	509.0	501.0
165°	553.4	549.5	545.5	543.0	540.6	533.7	527.7	519.8	511.9	505.0	499.1
167.5°	536.6	533.7	531.7	529.7	527.7	523.8	518.8	511.9	506.0	501.0	498.1
170°	521.8	519.8	518.8	517.8	516.9	512.9	509.9	505.0	500.1	497.1	495.1
172.5°	509.9	508.0	508.0	507.5	507.0	504.0	502.0	498.1	495.1	494.1	494.1
175°	499.1	498.1	498.1	498.1	498.1	496.1	495.1	493.1	491.2	491.2	492.2
177.5°	492.2	491.2	492.2	492.2	492.2	491.2	490.2	489.2	488.2	489.2	491.2
180°	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	548.3	546.0	543.8	543.8	538.8	534.2	532.0	532.9	530.2	526.5	522.9
5°	572.3	563.3	561.5	556.5	549.7	540.1	535.1	530.6	525.2	517.9	511.1
7.5°	594.6	582.8	576.4	571.4	558.3	545.1	534.2	527.0	517.5	506.6	498.4
10°	623.6	601.8	595.0	583.7	565.1	546.5	533.8	522.0	508.8	496.1	485.3
12.5°	646.7	621.8	609.1	597.7	573.7	550.1	528.8	514.3	498.4	484.4	470.3
15°	673.0	644.9	622.7	609.1	578.7	550.1	526.1	505.7	488.0	470.7	458.5
17.5°	685.7	650.3	640.4	620.9	576.9	548.3	518.8	497.1	475.7	455.8	441.3
20°	705.7	664.4	639.5	626.3	587.3	545.1	510.7	485.7	463.5	442.2	426.8
22.5°	707.0	662.1	645.8	620.9	572.8	535.6	503.4	473.0	447.2	427.2	411.3
25°	703.9	658.1	635.4	615.4	575.5	530.2	488.9	459.0	433.6	410.4	391.8
27.5°	702.5	646.3	624.9	605.0	560.1	514.3	480.3	446.3	417.2	396.8	377.8
30°	700.7	633.6	607.7	584.6	543.3	502.0	461.2	431.7	404.1	378.2	359.2
32.5°	688.9	616.3	590.0	565.5	521.1	479.8	447.6	416.3	386.4	362.4	345.1
35°	685.3	600.5	566.0	539.7	496.1	459.4	425.4	399.5	371.4	347.4	327.0
37.5°	674.8	584.1	546.9	513.4	468.0	433.1	408.2	382.3	355.1	329.3	312.9
40°	656.7	565.1	522.9	488.4	441.7	406.4	383.2	364.2	337.4	314.3	294.3
42.5°	629.9	545.6	500.2	463.9	412.2	379.1	360.1	342.0	319.3	295.2	278.9
45°	599.1	519.7	477.6	437.2	384.6	352.4	332.4	321.5	300.7	280.3	261.2
47.5°	556.9	493.0	451.2	409.5	356.0	324.7	308.8	298.0	283.4	261.2	245.8
50°	503.9	458.5	419.0	381.9	327.9	298.0	282.1	273.9	261.7	245.8	230.8
52.5°	444.9	418.6	385.9	351.5	299.3	271.2	256.7	250.3	241.3	226.3	213.6
55°	385.5	374.2	351.9	317.9	269.4	246.3	233.6	225.4	218.6	207.7	196.8
57.5°	332.4	327.0	311.6	285.3	244.4	220.4	209.5	204.1	198.6	190.5	179.6
60°	277.6	283.4	267.6	254.4	217.2	196.4	186.8	181.0	178.2	171.0	164.2
62.5°	229.9	235.4	226.3	216.3	190.0	171.4	165.5	160.1	158.3	151.9	145.1
65°	186.8	193.7	186.8	181.4	165.5	150.1	142.9	140.1	138.3	134.2	128.8
67.5°	148.8	155.6	152.4	145.6	140.6	127.9	123.8	121.1	120.2	117.0	112.5
70°	112.0	121.5	122.4	118.4	113.8	107.9	105.2	104.3	102.0	99.3	96.6
72.5°	80.7	91.6	92.1	92.1	89.3	89.3	86.6	85.3	85.3	82.5	79.4
75°	59.4	66.7	67.6	68.5	69.8	71.2	69.4	69.4	68.9	66.2	64.9
77.5°	39.5	45.8	48.1	51.2	53.1	53.1	54.0	54.9	54.0	52.6	51.7
80°	25.4	29.9	32.7	34.5	37.2	38.5	39.9	40.4	39.5	39.0	37.6
82.5°	16.8	18.1	19.5	21.8	24.9	27.2	27.2	26.8	27.7	27.2	26.8
85°	9.5	10.4	10.9	11.3	13.2	15.4	15.9	16.3	17.2	16.3	15.4
87.5°	3.6	4.1	4.1	4.1	5.0	5.4	6.8	8.6	8.2	7.3	7.3
90°	15.8	12.8	11.9	10.9	8.9	5.9	4.0	2.0	4.0	5.9	8.9
92.5°	99.8	68.2	59.3	50.4	40.5	31.6	21.7	14.8	21.7	31.6	40.5
95°	212.5	128.5	109.2	89.9	64.2	47.4	36.6	33.6	36.6	47.4	64.2
97.5°	229.3	146.3	125.0	103.8	78.1	63.2	54.4	53.4	54.4	63.2	78.1
100°	226.3	157.1	137.8	118.6	94.9	81.0	74.1	73.1	74.1	81.0	94.9
102.5°	230.3	170.0	152.7	135.4	114.6	101.8	95.9	93.9	95.9	101.8	114.6
105°	238.2	184.8	169.5	154.2	135.4	123.5	117.6	114.6	117.6	123.5	135.4
107.5°	251.0	203.6	189.2	174.9	157.1	145.3	139.3	136.4	139.3	145.3	157.1
110°	267.8	223.3	209.5	195.7	178.9	168.0	163.1	160.1	163.1	168.0	178.9

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	284.6	244.1	230.8	217.4	200.6	189.7	184.8	181.8	184.8	189.7	200.6
115°	303.4	265.8	252.5	239.2	222.4	212.5	206.5	202.6	206.5	212.5	222.4
117.5°	323.2	285.6	273.2	260.9	242.1	233.2	228.3	223.3	228.3	233.2	242.1
120°	341.9	306.4	294.0	281.7	262.9	253.0	248.1	245.1	248.1	253.0	262.9
122.5°	361.7	327.1	313.8	300.4	282.6	271.8	266.8	263.9	266.8	271.8	282.6
125°	380.5	345.9	332.5	319.2	300.4	289.6	283.6	281.7	283.6	289.6	300.4
127.5°	397.3	363.7	350.4	337.0	316.2	305.4	298.5	295.5	298.5	305.4	316.2
130°	412.1	379.5	366.2	352.8	332.1	320.2	311.3	308.3	311.3	320.2	332.1
132.5°	425.0	393.3	380.5	367.6	346.9	332.1	322.2	318.2	322.2	332.1	346.9
135°	437.8	407.2	393.8	380.5	359.7	344.9	334.0	330.1	334.0	344.9	359.7
137.5°	446.7	417.0	404.6	392.3	371.6	355.8	344.9	341.0	344.9	355.8	371.6
140°	455.6	426.9	414.6	402.2	382.5	366.6	356.8	351.8	356.8	366.6	382.5
142.5°	462.5	434.8	423.4	412.1	392.3	378.5	367.6	363.7	367.6	378.5	392.3
145°	468.4	442.7	431.4	420.0	403.2	388.4	379.5	376.5	379.5	388.4	403.2
147.5°	473.4	449.7	439.8	429.9	413.1	400.2	391.4	389.4	391.4	400.2	413.1
150°	478.3	455.6	446.7	437.8	424.0	411.1	403.2	402.2	403.2	411.1	424.0
152.5°	481.3	462.5	454.1	445.7	433.8	423.0	415.1	415.1	415.1	423.0	433.8
155°	485.2	468.4	461.5	454.6	443.7	433.8	427.9	427.9	427.9	433.8	443.7
157.5°	487.2	473.4	468.0	462.5	452.6	443.7	438.8	437.8	438.8	443.7	452.6
160°	490.2	478.3	473.4	468.4	461.5	453.6	449.7	449.7	449.7	453.6	461.5
162.5°	491.2	481.3	477.4	473.4	467.4	461.5	458.6	458.6	458.6	461.5	467.4
165°	492.2	484.2	480.8	477.3	473.4	468.4	466.5	467.4	466.5	468.4	473.4
167.5°	492.2	486.2	483.8	481.3	478.3	474.4	473.4	474.4	473.4	474.4	478.3
170°	491.2	486.2	485.2	484.2	482.3	479.3	478.3	480.3	478.3	479.3	482.3
172.5°	491.2	487.2	486.7	486.2	485.2	483.3	483.3	484.2	483.3	483.3	485.2
175°	490.2	488.2	487.7	487.2	487.2	485.2	486.2	487.2	486.2	485.2	487.2
177.5°	489.2	488.2	488.2	488.2	488.2	487.2	488.2	489.2	488.2	487.2	488.2
180°	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	522.9	520.6	519.7	517.5	512.0	508.4	504.3	501.6	502.0	499.8	501.1
5°	506.6	506.1	502.9	498.4	490.7	486.6	479.4	475.7	473.9	474.4	471.7
7.5°	493.0	488.9	486.6	479.4	472.1	463.5	457.6	454.4	451.7	449.0	447.2
10°	477.6	473.9	470.3	462.6	452.6	444.4	436.3	433.1	429.0	427.2	425.9
12.5°	461.2	459.0	454.4	445.4	434.0	426.3	416.8	415.0	409.5	405.9	405.0
15°	446.3	444.9	436.7	426.3	415.0	407.3	399.1	393.7	384.6	386.4	383.2
17.5°	430.4	424.5	419.5	405.4	400.0	388.2	378.7	376.0	369.6	365.5	361.5
20°	412.7	409.1	402.7	393.7	380.5	366.9	359.6	355.1	351.5	345.1	343.3
22.5°	395.9	391.4	385.9	374.2	362.8	351.5	341.5	337.4	332.9	328.3	325.6
25°	382.8	376.0	370.1	355.6	344.2	334.7	328.3	321.5	315.2	312.5	311.6
27.5°	362.4	358.3	352.4	338.8	328.3	317.9	312.0	307.5	300.7	297.5	294.8
30°	349.2	341.0	334.2	323.4	312.9	301.6	296.1	290.7	286.6	282.5	279.4
32.5°	331.5	325.2	319.7	308.8	298.4	288.0	282.1	273.9	271.7	268.5	264.9
35°	314.3	310.2	304.3	292.5	281.2	273.9	267.6	259.9	257.1	254.9	251.7
37.5°	298.0	292.1	288.0	276.6	266.7	258.1	253.1	246.7	244.9	242.2	239.9
40°	283.9	278.0	273.9	262.6	252.2	243.1	239.9	233.6	230.8	227.7	226.3
42.5°	268.0	263.0	257.6	249.4	238.5	229.5	223.1	219.5	215.9	214.5	211.8
45°	251.2	246.7	242.6	233.6	222.2	215.9	210.4	205.4	202.7	200.5	198.6
47.5°	236.7	232.7	227.2	217.2	208.2	202.3	196.8	191.8	189.1	186.4	184.1
50°	220.0	217.7	211.8	202.3	193.7	186.8	181.9	177.3	175.5	172.3	168.7
52.5°	205.0	200.9	195.9	188.2	180.5	172.3	165.5	162.8	159.6	157.8	154.6
55°	187.3	184.6	179.1	172.3	164.2	157.4	152.4	148.8	144.7	142.9	138.8
57.5°	172.3	167.3	164.6	156.0	148.3	141.5	137.9	134.2	129.7	127.0	125.2
60°	156.0	151.5	147.4	140.1	134.7	127.4	122.0	118.8	115.6	112.0	110.2
62.5°	140.1	136.5	131.5	125.6	118.8	112.9	108.8	104.3	102.5	98.9	97.5
65°	122.9	120.2	116.1	109.3	103.9	98.9	94.8	91.2	89.3	88.0	87.1
67.5°	107.5	103.9	101.1	95.2	89.3	85.3	83.0	80.7	78.5	77.1	75.7
70°	91.6	88.9	86.2	80.7	76.6	73.0	71.2	69.4	68.0	66.7	65.3
72.5°	75.3	73.9	71.2	67.6	64.4	61.7	60.3	58.1	56.7	54.4	53.5
75°	62.1	59.9	58.5	55.3	52.6	50.3	48.5	45.8	44.0	43.1	42.6
77.5°	49.0	48.1	46.3	43.5	42.2	39.9	37.2	36.3	35.4	35.4	34.9
80°	36.7	35.4	34.0	31.7	30.4	28.6	28.6	28.6	28.1	28.6	28.1
82.5°	24.9	24.0	23.1	21.8	21.3	21.3	21.8	21.8	21.8	21.8	21.8
85°	14.5	14.5	14.5	15.0	14.5	14.5	15.0	15.4	15.0	15.0	14.5
87.5°	6.8	6.8	7.3	7.3	7.7	7.7	7.7	7.7	7.7	7.7	8.2
90°	10.9	11.9	12.8	15.8	18.8	21.7	24.7	23.7	24.7	25.7	26.7
92.5°	50.4	59.3	68.2	99.8	152.2	203.6	183.8	137.4	97.8	76.1	66.2
95°	89.9	109.2	128.5	212.5	359.7	521.8	586.0	475.4	355.8	241.1	188.8
97.5°	103.8	125.0	146.3	229.3	400.2	673.0	901.3	931.9	817.3	616.7	486.2
100°	118.6	137.8	157.1	226.3	372.6	632.5	935.9	1130.6	1165.2	1085.1	969.5
102.5°	135.4	152.7	170.0	230.3	348.9	573.2	871.6	1140.5	1280.8	1297.6	1242.2
105°	154.2	169.5	184.8	238.2	340.0	526.7	794.6	1078.2	1284.7	1383.6	1402.3
107.5°	174.9	189.2	203.6	251.0	338.0	493.1	726.4	989.2	1225.4	1380.6	1457.7
110°	195.7	209.5	223.3	267.8	342.9	475.4	670.0	906.2	1132.5	1314.4	1438.9

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	217.4	230.8	244.1	284.6	352.8	465.5	632.5	834.1	1040.6	1227.4	1370.7
115°	239.2	252.5	265.8	303.4	363.7	464.5	607.8	778.7	961.6	1133.5	1278.8
117.5°	260.9	273.2	285.6	323.2	377.5	465.5	591.0	742.2	900.3	1052.5	1185.9
120°	281.7	294.0	306.4	341.9	393.3	469.4	580.1	714.5	853.9	987.3	1105.9
122.5°	300.4	313.8	327.1	361.7	408.2	476.3	573.2	691.8	817.3	934.9	1042.6
125°	319.2	332.5	345.9	380.5	424.0	483.3	567.3	673.0	785.7	893.4	988.3
127.5°	337.0	350.4	363.7	397.3	436.8	491.2	564.3	655.2	757.0	854.8	941.8
130°	352.8	366.2	379.5	412.1	449.7	499.1	561.3	641.4	730.3	819.3	899.3
132.5°	367.6	380.5	393.3	425.0	461.5	505.0	560.3	628.5	705.6	785.7	858.8
135°	380.5	393.8	407.2	437.8	471.4	510.9	559.4	617.7	683.9	754.0	818.3
137.5°	392.3	404.6	417.0	446.7	479.3	514.9	557.4	607.8	663.1	722.4	779.7
140°	402.2	414.6	426.9	455.6	485.2	518.8	556.4	598.9	645.3	695.7	743.2
142.5°	412.1	423.4	434.8	462.5	491.2	521.8	554.4	591.0	628.5	670.0	709.6
145°	420.0	431.4	442.7	468.4	495.1	522.8	552.4	584.1	615.7	648.3	679.9
147.5°	429.9	439.8	449.7	473.4	498.1	522.8	549.5	577.1	604.8	631.5	658.2
150°	437.8	446.7	455.6	478.3	499.1	522.8	545.5	570.2	593.0	615.7	636.4
152.5°	445.7	454.1	462.5	481.3	501.0	519.8	540.6	562.3	582.1	600.9	618.7
155°	454.6	461.5	468.4	485.2	501.0	517.8	534.6	554.4	571.2	587.0	601.9
157.5°	462.5	468.0	473.4	487.2	502.0	514.9	529.7	545.5	559.4	573.2	585.1
160°	468.4	473.4	478.3	490.2	502.0	512.9	523.8	536.6	549.5	560.3	570.2
162.5°	473.4	477.4	481.3	491.2	501.0	509.0	517.8	527.7	537.6	546.5	555.4
165°	477.3	480.8	484.2	492.2	499.1	505.0	511.9	519.8	527.7	533.7	540.6
167.5°	481.3	483.8	486.2	492.2	498.1	501.0	506.0	511.9	518.8	523.8	527.7
170°	484.2	485.2	486.2	491.2	495.1	497.1	500.1	505.0	509.9	512.9	516.9
172.5°	486.2	486.7	487.2	491.2	494.1	494.1	495.1	498.1	502.0	504.0	507.0
175°	487.2	487.7	488.2	490.2	492.2	491.2	491.2	493.1	495.1	496.1	498.1
177.5°	488.2	488.2	488.2	489.2	491.2	489.2	488.2	489.2	490.2	491.2	492.2
180°	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	500.7	501.1	499.8	497.1	496.6	497.5	500.2	499.3	497.1	501.1	497.5
5°	473.0	470.7	469.8	470.7	468.0	466.7	469.4	468.0	469.4	469.8	471.2
7.5°	446.3	446.7	444.0	444.4	440.8	441.7	441.7	441.7	443.1	444.0	445.8
10°	423.1	424.0	420.9	421.3	418.6	416.8	418.1	420.9	420.9	420.9	421.8
12.5°	404.5	400.5	398.2	397.7	394.6	393.7	396.4	397.3	399.5	399.5	400.9
15°	381.4	380.5	378.7	378.7	371.0	372.8	373.7	376.9	381.4	377.8	378.7
17.5°	360.5	358.3	356.0	355.1	354.2	351.5	355.1	354.6	357.4	357.8	359.2
20°	342.0	340.1	335.6	336.1	337.0	332.9	335.1	335.1	337.9	340.6	343.8
22.5°	323.8	322.0	319.7	320.6	317.9	317.0	317.0	319.3	322.5	324.7	324.3
25°	309.8	306.6	305.2	303.9	302.5	303.4	302.0	304.3	306.6	307.9	306.6
27.5°	293.9	292.5	289.8	288.4	286.2	287.1	288.0	289.8	291.2	291.2	292.5
30°	278.5	276.6	275.7	274.4	274.4	272.6	273.0	274.8	276.2	277.6	279.4
32.5°	263.5	262.1	260.8	260.8	259.9	259.4	259.0	261.7	261.7	264.4	264.4
35°	251.2	249.0	249.0	246.7	247.6	247.2	246.3	248.1	248.5	250.3	249.9
37.5°	237.6	237.6	236.7	234.5	232.7	233.1	235.4	235.4	236.7	236.3	237.6
40°	224.0	223.1	223.1	221.8	221.3	220.9	221.3	221.8	224.0	223.6	224.0
42.5°	210.4	210.9	208.6	208.6	208.6	207.3	207.7	208.2	209.1	210.0	211.3
45°	197.3	196.4	195.9	195.0	194.1	194.6	194.1	195.9	195.5	196.4	197.7
47.5°	183.2	181.9	181.4	179.6	179.6	180.5	180.0	181.4	181.9	183.2	182.3
50°	169.6	167.8	166.4	166.9	164.2	165.1	165.1	166.4	167.8	168.3	169.2
52.5°	153.7	153.3	152.8	150.6	150.1	149.7	150.1	150.6	152.4	153.7	154.2
55°	138.3	137.9	135.1	134.2	132.9	132.9	133.8	134.2	137.4	137.9	139.7
57.5°	124.3	122.9	119.7	119.3	119.3	119.3	117.9	119.7	120.6	122.9	122.9
60°	108.8	108.8	106.1	106.1	106.6	106.1	106.1	106.6	106.6	108.4	109.3
62.5°	96.6	96.1	96.1	95.2	94.8	95.2	94.8	94.8	95.2	96.6	98.0
65°	85.7	85.3	84.8	84.4	83.4	83.4	83.9	84.8	84.8	85.7	86.2
67.5°	75.3	75.3	74.4	74.4	73.9	73.5	73.9	73.5	75.3	75.3	75.7
70°	64.9	64.4	63.0	62.6	61.2	61.7	61.7	63.0	63.5	64.4	65.3
72.5°	52.2	52.2	51.2	50.3	50.8	49.9	49.9	50.3	50.3	51.7	52.2
75°	43.1	42.2	41.7	42.2	41.7	42.6	41.7	41.7	42.6	42.6	42.6
77.5°	35.4	35.4	34.9	34.9	35.4	34.9	35.4	35.4	35.4	34.9	35.4
80°	29.0	28.6	28.6	28.6	28.1	28.1	28.1	28.1	28.1	28.1	28.1
82.5°	21.8	21.8	21.3	21.8	21.8	21.3	21.8	21.3	21.3	21.8	21.8
85°	14.5	15.4	14.5	14.5	15.0	15.0	15.4	15.0	15.4	14.5	15.0
87.5°	7.7	8.2	8.2	7.7	7.7	8.2	8.2	8.2	8.6	7.7	8.2
90°	27.7	28.7	27.7	28.7	29.6	28.7	29.6	28.7	27.7	28.7	27.7
92.5°	62.8	59.3	57.3	53.4	54.4	52.4	54.4	53.4	57.3	59.3	62.8
95°	171.0	153.2	134.4	125.5	118.6	114.6	118.6	125.5	134.4	153.2	171.0
97.5°	429.9	373.6	307.3	269.8	246.1	235.2	246.1	269.8	307.3	373.6	429.9
100°	899.4	829.2	729.3	657.2	618.7	619.6	618.7	657.2	729.3	829.2	899.4
102.5°	1204.2	1166.1	1094.0	1040.6	1010.0	981.3	1010.0	1040.6	1094.0	1166.1	1204.2
105°	1389.4	1376.6	1331.2	1293.6	1262.0	1257.1	1262.0	1293.6	1331.2	1376.6	1389.4
107.5°	1471.1	1484.4	1478.4	1460.6	1447.8	1436.9	1447.8	1460.6	1478.4	1484.4	1471.1
110°	1473.5	1508.1	1535.8	1543.7	1541.7	1539.7	1541.7	1543.7	1535.8	1508.1	1473.5

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1417.6	1464.6	1520.9	1549.6	1559.5	1560.5	1559.5	1549.6	1520.9	1464.6	1417.6
115°	1332.6	1386.5	1460.6	1504.1	1523.9	1528.8	1523.9	1504.1	1460.6	1386.5	1332.6
117.5°	1241.8	1297.6	1374.7	1423.1	1452.7	1459.7	1452.7	1423.1	1374.7	1297.6	1241.8
120°	1155.8	1205.7	1283.8	1339.1	1362.8	1368.7	1362.8	1339.1	1283.8	1205.7	1155.8
122.5°	1088.0	1133.5	1200.7	1249.2	1275.8	1283.8	1275.8	1249.2	1200.7	1133.5	1088.0
125°	1027.8	1067.3	1130.6	1174.1	1198.8	1205.7	1198.8	1174.1	1130.6	1067.3	1027.8
127.5°	978.4	1014.9	1072.3	1109.8	1132.5	1138.5	1132.5	1109.8	1072.3	1014.9	978.4
130°	932.9	966.5	1018.9	1054.5	1075.2	1083.1	1075.2	1054.5	1018.9	966.5	932.9
132.5°	890.4	922.0	970.5	1006.0	1023.8	1028.8	1023.8	1006.0	970.5	922.0	890.4
135°	846.4	874.6	923.0	952.7	970.5	977.4	970.5	952.7	923.0	874.6	846.4
137.5°	804.9	830.1	871.6	902.3	917.1	923.0	917.1	902.3	871.6	830.1	804.9
140°	764.4	785.7	823.2	850.9	866.7	865.7	866.7	850.9	823.2	785.7	764.4
142.5°	727.4	745.1	775.8	799.5	813.3	812.4	813.3	799.5	775.8	745.1	727.4
145°	694.2	708.6	733.3	754.0	761.9	763.9	761.9	754.0	733.3	708.6	694.2
147.5°	668.6	678.9	698.7	713.5	721.4	722.4	721.4	713.5	698.7	678.9	668.6
150°	645.8	655.2	670.0	680.9	686.8	686.8	686.8	680.9	670.0	655.2	645.8
152.5°	626.1	633.5	644.3	654.2	657.2	657.2	657.2	654.2	644.3	633.5	626.1
155°	607.8	613.7	622.6	630.5	632.5	633.5	632.5	630.5	622.6	613.7	607.8
157.5°	590.0	594.9	602.8	608.8	610.7	610.7	610.7	608.8	602.8	594.9	590.0
160°	573.7	577.1	584.1	590.0	590.0	589.0	590.0	590.0	584.1	577.1	573.7
162.5°	558.3	561.3	565.3	570.2	570.2	569.2	570.2	570.2	565.3	561.3	558.3
165°	543.0	545.5	549.5	553.4	552.4	552.4	552.4	553.4	549.5	545.5	543.0
167.5°	529.7	531.7	533.7	536.6	535.6	535.6	535.6	536.6	533.7	531.7	529.7
170°	517.8	518.8	519.8	521.8	520.8	520.8	520.8	521.8	519.8	518.8	517.8
172.5°	507.5	508.0	508.0	509.9	508.0	507.0	508.0	509.9	508.0	508.0	507.5
175°	498.1	498.1	498.1	499.1	498.1	497.1	498.1	499.1	498.1	498.1	498.1
177.5°	492.2	492.2	491.2	492.2	490.2	490.2	490.2	492.2	491.2	492.2	492.2
180°	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	501.1	502.9	501.1	497.5	501.1	503.4	505.7	509.3	511.1	511.1	513.8
5°	472.6	476.2	474.8	473.9	477.6	479.8	483.4	488.0	493.0	496.1	499.8
7.5°	447.2	449.4	451.7	451.7	455.3	460.3	465.8	471.2	477.6	482.1	484.8
10°	424.9	426.8	428.1	429.9	435.4	440.8	448.1	454.9	460.3	465.3	469.8
12.5°	403.6	406.4	409.5	410.9	415.0	421.8	428.6	436.7	445.4	450.3	454.9
15°	383.2	384.6	388.2	392.3	395.9	403.2	411.8	420.4	427.7	435.4	439.5
17.5°	362.4	362.8	372.3	370.1	381.9	388.7	393.2	401.4	413.2	419.5	425.9
20°	342.0	346.5	350.6	352.8	359.2	366.9	380.0	386.4	395.9	401.8	407.3
22.5°	326.1	332.9	332.9	338.3	341.5	348.8	358.3	370.5	381.0	385.0	392.7
25°	312.0	315.2	320.6	322.5	328.3	334.7	341.0	354.2	365.5	371.0	376.4
27.5°	293.9	298.0	305.2	305.2	312.9	319.7	327.4	336.1	347.4	355.1	361.0
30°	279.8	283.9	287.1	292.1	295.2	301.6	315.2	321.5	331.5	338.3	345.6
32.5°	266.7	269.8	272.6	278.0	281.6	288.9	296.1	307.5	316.1	322.5	330.2
35°	252.2	255.3	259.0	263.0	268.5	275.3	282.1	291.6	300.2	306.1	312.5
37.5°	238.5	240.8	246.3	249.0	253.5	259.9	268.5	278.5	286.2	290.7	297.1
40°	225.4	227.2	231.3	236.3	239.5	244.4	253.5	262.1	271.7	277.1	282.1
42.5°	211.3	213.6	217.2	222.2	227.2	232.7	237.6	247.6	256.2	260.8	266.2
45°	199.1	200.5	203.2	208.2	213.2	217.2	224.9	234.0	242.2	245.8	251.7
47.5°	184.6	185.9	190.0	192.3	197.7	203.2	210.9	220.0	227.2	230.8	236.3
50°	169.6	171.0	173.7	178.7	182.3	188.2	195.0	202.7	211.8	216.8	220.0
52.5°	155.1	157.8	160.1	164.2	168.7	174.6	181.0	188.2	195.9	200.9	204.5
55°	140.6	142.9	145.6	147.8	153.3	158.7	166.0	172.8	179.6	184.1	188.2
57.5°	124.3	127.4	130.2	134.7	138.8	143.3	151.5	156.9	165.1	168.3	171.9
60°	110.2	113.4	115.6	119.3	122.9	128.8	134.2	141.0	147.8	151.9	156.5
62.5°	98.4	99.8	101.1	104.8	108.4	113.8	119.3	126.1	133.3	135.6	139.2
65°	86.6	88.0	90.2	93.4	96.1	99.3	105.2	110.7	117.5	121.1	122.4
67.5°	76.6	78.0	78.5	80.7	83.0	86.6	89.8	95.2	101.6	103.9	106.6
70°	65.3	67.6	68.0	69.8	70.7	73.0	76.6	80.7	85.7	89.8	92.1
72.5°	52.2	55.3	56.2	59.0	60.3	62.6	65.3	68.5	71.7	73.5	75.3
75°	42.6	43.5	44.0	46.3	48.5	51.7	53.1	54.9	57.6	59.9	61.7
77.5°	35.4	35.8	36.3	36.3	36.7	38.5	41.3	43.5	45.4	46.3	47.6
80°	28.6	28.1	28.1	28.6	28.6	28.6	29.5	32.7	33.6	35.8	35.4
82.5°	22.2	21.3	21.8	21.3	21.3	21.3	21.3	21.8	21.8	23.1	24.0
85°	14.5	15.0	14.5	14.5	14.1	14.5	14.1	14.1	13.6	13.6	13.2
87.5°	7.7	8.2	7.7	7.7	7.3	7.7	7.3	7.3	6.8	6.8	5.9
90°	26.7	25.7	24.7	23.7	24.7	21.7	18.8	15.8	12.8	11.9	10.9
92.5°	66.2	76.1	97.8	137.4	183.8	203.6	152.2	99.8	68.2	59.3	50.4
95°	188.8	241.1	355.8	475.4	586.0	521.8	359.7	212.5	128.5	109.2	89.9
97.5°	486.2	616.7	817.3	931.9	901.3	673.0	400.2	229.3	146.3	125.0	103.8
100°	969.5	1085.1	1165.2	1130.6	935.9	632.5	372.6	226.3	157.1	137.8	118.6
102.5°	1242.2	1297.6	1280.8	1140.5	871.6	573.2	348.9	230.3	170.0	152.7	135.4
105°	1402.3	1383.6	1284.7	1078.2	794.6	526.7	340.0	238.2	184.8	169.5	154.2
107.5°	1457.7	1380.6	1225.4	989.2	726.4	493.1	338.0	251.0	203.6	189.2	174.9
110°	1438.9	1314.4	1132.5	906.2	670.0	475.4	342.9	267.8	223.3	209.5	195.7

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1370.7	1227.4	1040.6	834.1	632.5	465.5	352.8	284.6	244.1	230.8	217.4
115°	1278.8	1133.5	961.6	778.7	607.8	464.5	363.7	303.4	265.8	252.5	239.2
117.5°	1185.9	1052.5	900.3	742.2	591.0	465.5	377.5	323.2	285.6	273.2	260.9
120°	1105.9	987.3	853.9	714.5	580.1	469.4	393.3	341.9	306.4	294.0	281.7
122.5°	1042.6	934.9	817.3	691.8	573.2	476.3	408.2	361.7	327.1	313.8	300.4
125°	988.3	893.4	785.7	673.0	567.3	483.3	424.0	380.5	345.9	332.5	319.2
127.5°	941.8	854.8	757.0	655.2	564.3	491.2	436.8	397.3	363.7	350.4	337.0
130°	899.3	819.3	730.3	641.4	561.3	499.1	449.7	412.1	379.5	366.2	352.8
132.5°	858.8	785.7	705.6	628.5	560.3	505.0	461.5	425.0	393.3	380.5	367.6
135°	818.3	754.0	683.9	617.7	559.4	510.9	471.4	437.8	407.2	393.8	380.5
137.5°	779.7	722.4	663.1	607.8	557.4	514.9	479.3	446.7	417.0	404.6	392.3
140°	743.2	695.7	645.3	598.9	556.4	518.8	485.2	455.6	426.9	414.6	402.2
142.5°	709.6	670.0	628.5	591.0	554.4	521.8	491.2	462.5	434.8	423.4	412.1
145°	679.9	648.3	615.7	584.1	552.4	522.8	495.1	468.4	442.7	431.4	420.0
147.5°	658.2	631.5	604.8	577.1	549.5	522.8	498.1	473.4	449.7	439.8	429.9
150°	636.4	615.7	593.0	570.2	545.5	522.8	499.1	478.3	455.6	446.7	437.8
152.5°	618.7	600.9	582.1	562.3	540.6	519.8	501.0	481.3	462.5	454.1	445.7
155°	601.9	587.0	571.2	554.4	534.6	517.8	501.0	485.2	468.4	461.5	454.6
157.5°	585.1	573.2	559.4	545.5	529.7	514.9	502.0	487.2	473.4	468.0	462.5
160°	570.2	560.3	549.5	536.6	523.8	512.9	502.0	490.2	478.3	473.4	468.4
162.5°	555.4	546.5	537.6	527.7	517.8	509.0	501.0	491.2	481.3	477.4	473.4
165°	540.6	533.7	527.7	519.8	511.9	505.0	499.1	492.2	484.2	480.8	477.3
167.5°	527.7	523.8	518.8	511.9	506.0	501.0	498.1	492.2	486.2	483.8	481.3
170°	516.9	512.9	509.9	505.0	500.1	497.1	495.1	491.2	486.2	485.2	484.2
172.5°	507.0	504.0	502.0	498.1	495.1	494.1	494.1	491.2	487.2	486.7	486.2
175°	498.1	496.1	495.1	493.1	491.2	491.2	492.2	490.2	488.2	487.7	487.2
177.5°	492.2	491.2	490.2	489.2	488.2	489.2	491.2	489.2	488.2	488.2	488.2
180°	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2	488.2

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	529.7	529.7	529.7	529.7
2.5°	516.1	519.3	525.6	531.1
5°	505.2	510.2	519.7	529.3
7.5°	492.1	499.8	512.0	525.2
10°	479.4	489.3	504.3	519.7
12.5°	466.7	477.1	493.0	512.9
15°	451.7	462.6	481.6	505.7
17.5°	438.6	453.1	470.3	494.3
20°	424.5	435.4	457.6	483.0
22.5°	406.8	424.9	445.8	472.6
25°	392.7	408.6	429.5	459.9
27.5°	375.5	394.1	419.5	446.3
30°	361.5	376.9	400.5	432.7
32.5°	345.1	363.3	387.8	419.5
35°	330.6	346.0	369.2	401.4
37.5°	313.4	330.2	356.0	384.6
40°	298.4	314.7	339.2	366.0
42.5°	280.3	297.5	322.0	344.7
45°	265.8	281.6	301.1	322.0
47.5°	248.1	264.9	283.9	298.4
50°	232.2	247.6	262.6	274.8
52.5°	215.0	229.0	242.6	251.7
55°	199.1	210.0	220.9	227.2
57.5°	180.5	190.9	200.0	203.6
60°	164.2	172.8	178.7	182.8
62.5°	146.9	153.3	157.8	160.1
65°	130.2	134.7	137.0	139.2
67.5°	112.9	117.0	118.4	121.1
70°	94.8	99.3	100.2	101.6
72.5°	81.2	81.2	83.0	84.8
75°	64.9	65.8	66.7	66.7
77.5°	50.8	50.8	51.7	52.2
80°	37.2	37.6	37.6	37.2
82.5°	25.4	26.3	25.4	24.9
85°	14.1	15.9	15.0	15.0
87.5°	5.9	5.9	6.8	5.9
90°	8.9	5.9	4.0	2.0
92.5°	40.5	31.6	21.7	14.8
95°	64.2	47.4	36.6	33.6
97.5°	78.1	63.2	54.4	53.4
100°	94.9	81.0	74.1	73.1
102.5°	114.6	101.8	95.9	93.9
105°	135.4	123.5	117.6	114.6
107.5°	157.1	145.3	139.3	136.4
110°	178.9	168.0	163.1	160.1

TEST NUMBER: P1012414

CATALOG NUMBER: S123RDIP-B340D1025UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	200.6	189.7	184.8	181.8
115°	222.4	212.5	206.5	202.6
117.5°	242.1	233.2	228.3	223.3
120°	262.9	253.0	248.1	245.1
122.5°	282.6	271.8	266.8	263.9
125°	300.4	289.6	283.6	281.7
127.5°	316.2	305.4	298.5	295.5
130°	332.1	320.2	311.3	308.3
132.5°	346.9	332.1	322.2	318.2
135°	359.7	344.9	334.0	330.1
137.5°	371.6	355.8	344.9	341.0
140°	382.5	366.6	356.8	351.8
142.5°	392.3	378.5	367.6	363.7
145°	403.2	388.4	379.5	376.5
147.5°	413.1	400.2	391.4	389.4
150°	424.0	411.1	403.2	402.2
152.5°	433.8	423.0	415.1	415.1
155°	443.7	433.8	427.9	427.9
157.5°	452.6	443.7	438.8	437.8
160°	461.5	453.6	449.7	449.7
162.5°	467.4	461.5	458.6	458.6
165°	473.4	468.4	466.5	467.4
167.5°	478.3	474.4	473.4	474.4
170°	482.3	479.3	478.3	480.3
172.5°	485.2	483.3	483.3	484.2
175°	487.2	485.2	486.2	487.2
177.5°	488.2	487.2	488.2	489.2
180°	488.2	488.2	488.2	488.2

(END OF REPORT)