

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012426

Luminaire Tested: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012426
REPORT IS A COMBINATION OF REPORTS P993149 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4966.0 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot





TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	26			
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23			
2	85	78	72	67	75	70	65	61	55	51	49	41	38	37	28	26	25	20			
3	77	69	62	56	69	62	56	51	48	44	41	36	34	31	25	23	22	17			
4	71	61	53	48	63	55	48	43	43	39	35	32	29	27	22	21	19	15			
5	65	54	47	41	58	49	42	37	39	34	30	29	26	24	20	18	17	13			
6	60	49	41	35	53	44	37	32	35	30	26	26	23	21	18	16	15	12			
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	10			
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	15	13	12	9			
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11	9			
10	44	33	26	22	40	30	24	20	24	20	16	18	15	13	13	11	10	8			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5672	5672	5672	5672
5°	5675	6532	5690	4846
10°	5626	7885	5650	4233
15°	5568	8949	5568	3732
20°	5453	9653	5484	3311
25°	5370	9171	5359	3021
30°	5273	6354	5262	2737
35°	5155	4079	5132	2524
40°	5010	2880	4985	2311
45°	4757	2305	4749	2104
50°	4446	1929	4431	1862
55°	4095	1590	4062	1579
60°	3751	1314	3714	1343
65°	3348	1052	3370	1138
70°	2974	730	3057	921
75°	2522	542	2625	707
80°	2009	358	2177	531
85°	1431	171	1556	330

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7571 cd/sqm

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.7	1.0
10°-20°	162.0	3.3
20°-30°	255.1	5.1
30°-40°	265.3	5.3
40°-50°	226.9	4.6
50°-60°	173.0	3.5
60°-70°	110.9	2.2
70°-80°	53.1	1.1
80°-90°	16.7	0.3
90°-100°	263.4	5.3
100°-110°	771.2	15.5
110°-120°	753.1	15.2
120°-130°	599.7	12.1
130°-140°	473.2	9.5
140°-150°	353.0	7.1
150°-160°	246.1	5.0
160°-170°	144.6	2.9
170°-180°	47.0	0.9
0°-30°	468.8	9.4
0°-40°	734.1	14.8
0°-60°	1134.1	22.8
0°-90°	1314.7	26.5
90°-120°	1787.6	36.0
90°-150°	3213.6	64.7
90°-180°	3651.0	73.5
0°-180°	4966.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	526	626	528	464	526	50
15°	503	889	503	371	503	141
25°	457	916	456	302	457	211
35°	399	397	397	246	399	250
45°	320	212	320	194	320	247
55°	226	133	224	132	226	203
65°	138	77	139	83	138	138
75°	66	32	69	42	66	72
85°	15	8	16	15	15	17
90°	2	28	2	28	2	3
95°	33	114	33	114	33	35
105°	114	1250	114	1250	114	121
115°	201	1520	201	1520	201	199
125°	280	1199	280	1199	280	249
135°	328	972	328	972	328	254
145°	374	760	374	760	374	235
155°	426	630	426	630	426	196
165°	465	549	465	549	465	131
175°	484	494	484	494	484	46
180°	485	485	485	485	485	

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	528.2	531.9	534.6	536.4	540.9	543.6	545.8	549.9	549.9	550.8	552.6
5°	526.4	534.1	539.5	546.7	556.2	560.7	567.0	572.5	580.1	584.2	588.2
7.5°	522.4	533.2	544.5	555.3	569.3	578.3	584.6	598.6	608.5	620.7	630.2
10°	517.0	531.9	546.3	563.0	581.9	595.5	604.9	623.4	642.4	659.5	674.0
12.5°	510.2	528.2	549.0	569.3	595.9	609.4	624.8	647.8	674.9	696.5	715.9
15°	503.0	523.7	547.2	572.0	605.4	624.3	646.4	674.4	704.6	735.8	762.4
17.5°	491.7	517.9	544.0	580.1	619.4	630.7	649.6	687.9	725.4	753.4	785.8
20°	480.4	509.8	542.7	575.2	617.6	643.7	661.3	701.9	742.1	775.9	807.0
22.5°	470.1	500.7	535.0	576.1	615.8	641.9	664.0	706.4	752.9	790.8	829.1
25°	457.4	490.8	528.7	567.5	615.8	635.6	660.0	709.1	758.3	802.1	849.4
27.5°	443.9	477.7	515.2	554.9	599.1	628.4	652.3	705.1	765.1	812.0	860.7
30°	430.4	465.1	501.2	536.8	586.4	614.4	641.9	700.1	768.7	822.4	859.8
32.5°	417.3	446.6	482.2	517.0	566.1	596.8	627.9	695.2	770.0	815.2	833.2
35°	399.2	429.9	458.8	495.8	545.4	575.6	612.2	694.7	764.2	792.1	783.1
37.5°	382.5	408.3	435.8	468.7	519.7	558.9	596.8	683.0	744.8	746.6	695.6
40°	364.0	385.2	408.3	443.0	498.0	536.8	577.9	664.9	709.6	683.0	593.2
42.5°	342.8	361.8	379.8	413.7	473.7	517.0	561.2	642.4	658.6	597.3	503.9
45°	320.3	335.6	352.3	388.0	448.0	490.8	535.0	607.6	591.0	504.3	415.5
47.5°	296.8	309.9	326.2	358.6	420.4	464.2	506.1	558.0	515.6	422.7	348.3
50°	273.4	283.7	299.5	332.9	392.5	432.2	471.0	504.8	445.2	362.7	287.8
52.5°	250.4	258.5	274.7	303.1	360.9	398.8	426.7	439.8	379.4	299.5	249.9
55°	226.0	235.0	245.9	274.7	332.0	360.0	378.5	378.0	315.8	254.0	206.6
57.5°	202.5	210.7	220.1	249.0	295.5	314.4	330.2	322.5	263.4	208.0	177.3
60°	181.8	186.3	196.7	221.0	256.2	272.5	281.5	268.4	215.2	175.5	146.6
62.5°	159.2	163.8	172.3	195.3	217.0	225.6	233.2	216.5	177.7	143.0	125.4
65°	138.5	144.4	149.8	168.3	180.0	190.4	189.5	175.5	138.9	116.4	102.0
67.5°	120.4	122.7	127.2	138.5	143.9	151.6	152.0	136.2	111.9	94.7	86.2
70°	101.0	103.3	106.5	111.9	115.5	117.3	116.4	102.4	84.4	74.0	66.3
72.5°	84.4	83.9	86.2	86.2	89.8	89.3	86.6	75.8	64.1	55.5	51.0
75°	66.3	66.8	67.2	66.3	65.0	63.2	60.9	52.8	45.1	41.1	37.0
77.5°	51.9	51.0	51.4	48.3	46.5	44.7	41.5	37.4	31.1	30.2	28.4
80°	37.0	36.5	36.1	34.7	30.7	28.9	26.6	24.4	23.0	22.1	21.7
82.5°	24.8	24.8	23.9	21.2	18.9	17.6	17.1	16.2	14.9	14.9	14.4
85°	14.9	14.4	13.5	10.8	9.5	9.5	9.5	9.5	8.6	8.6	8.1
87.5°	5.9	5.4	4.1	4.1	3.6	3.6	3.6	3.2	3.2	2.7	2.7
90°	2.0	3.9	5.9	8.8	10.8	11.8	12.8	15.7	18.7	21.6	24.6
92.5°	14.7	21.6	31.4	40.3	50.1	59.0	67.8	99.2	151.3	202.4	182.8
95°	33.4	36.4	47.2	63.9	89.4	108.6	127.7	211.3	357.7	518.8	582.7
97.5°	53.1	54.0	62.9	77.6	103.2	124.3	145.4	228.0	398.0	669.2	896.1
100°	72.7	73.7	80.6	94.3	117.9	137.0	156.2	225.0	370.4	628.9	930.5
102.5°	93.3	95.3	101.2	114.0	134.6	151.8	169.0	228.9	346.9	569.9	866.7
105°	114.0	116.9	122.8	134.6	153.3	168.5	183.7	236.8	338.0	523.7	790.0
107.5°	135.6	138.5	144.4	156.2	173.9	188.2	202.4	249.6	336.1	490.3	722.2
110°	159.2	162.1	167.0	177.9	194.6	208.4	222.1	266.3	341.0	472.6	666.2

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	180.8	183.7	188.7	199.5	216.2	229.4	242.7	283.0	350.8	462.8	628.9
115°	201.4	205.4	211.3	221.1	237.8	251.0	264.3	301.7	361.6	461.8	604.3
117.5°	222.1	227.0	231.9	240.7	259.4	271.7	284.0	321.3	375.4	462.8	587.6
120°	243.7	246.6	251.5	261.4	280.0	292.3	304.6	340.0	391.1	466.7	576.8
122.5°	262.4	265.3	270.2	281.0	298.7	312.0	325.2	359.6	405.8	473.6	569.9
125°	280.0	282.0	287.9	298.7	317.4	330.6	343.9	378.3	421.5	480.5	564.0
127.5°	293.8	296.7	303.6	314.4	335.1	348.4	361.6	395.0	434.3	488.4	561.1
130°	306.6	309.5	318.4	330.2	350.8	364.0	377.3	409.7	447.1	496.2	558.1
132.5°	316.4	320.3	330.2	344.9	365.5	378.3	391.1	422.5	458.9	502.1	557.1
135°	328.2	332.1	342.9	357.7	378.3	391.6	404.8	435.3	468.7	508.0	556.2
137.5°	339.0	342.9	353.7	369.5	390.1	402.4	414.7	444.1	476.6	511.9	554.2
140°	349.8	354.7	364.5	380.3	399.9	412.2	424.5	453.0	482.5	515.9	553.2
142.5°	361.6	365.5	376.3	390.1	409.7	421.0	432.4	459.9	488.4	518.8	551.2
145°	374.4	377.3	386.2	400.9	417.6	428.9	440.2	465.8	492.3	519.8	549.3
147.5°	387.1	389.1	398.0	410.7	427.4	437.2	447.1	470.7	495.2	519.8	546.3
150°	399.9	400.9	408.8	421.5	435.3	444.2	453.0	475.6	496.2	519.8	542.4
152.5°	412.7	412.7	420.6	431.4	443.2	451.6	459.9	478.5	498.2	516.9	537.5
155°	425.5	425.5	431.4	441.2	452.0	458.9	465.8	482.5	498.2	514.9	531.6
157.5°	435.3	436.3	441.2	450.0	459.9	465.3	470.7	484.4	499.2	511.9	526.7
160°	447.1	447.1	451.0	458.9	465.8	470.7	475.6	487.4	499.2	510.0	520.8
162.5°	455.9	455.9	458.9	464.8	470.7	474.6	478.5	488.4	498.2	506.0	514.9
165°	464.8	463.8	465.8	470.7	474.6	478.0	481.5	489.3	496.2	502.1	509.0
167.5°	471.7	470.7	471.7	475.6	478.5	481.0	483.4	489.3	495.2	498.2	503.1
170°	477.6	475.6	476.6	479.5	481.5	482.4	483.4	488.4	492.3	494.3	497.2
172.5°	481.5	480.5	480.5	482.5	483.4	483.9	484.4	488.4	491.3	491.3	492.3
175°	484.4	483.4	482.5	484.4	484.4	484.9	485.4	487.4	489.3	488.4	488.4
177.5°	486.4	485.4	484.4	485.4	485.4	485.4	485.4	486.4	488.4	486.4	485.4
180°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	556.2	556.2	560.3	564.3	562.1	563.4	568.4	566.6	570.2	569.8	571.1
5°	598.2	603.1	607.2	615.8	617.1	615.8	624.3	626.6	630.7	625.7	627.9
7.5°	645.5	655.9	665.8	678.5	682.5	683.4	687.9	694.3	699.7	689.7	694.7
10°	691.6	707.3	727.6	738.9	748.8	752.5	756.1	760.1	766.4	772.3	767.8
12.5°	741.2	764.2	783.6	803.9	816.1	814.7	825.1	827.8	832.7	834.1	835.9
15°	781.8	814.3	826.4	856.7	859.4	868.4	880.1	890.5	891.8	889.1	889.1
17.5°	820.6	848.5	870.2	894.6	899.5	907.2	922.1	927.0	928.8	928.4	928.4
20°	852.1	870.6	907.2	927.5	935.6	945.5	955.9	962.2	963.6	965.4	962.7
22.5°	872.9	900.9	930.6	947.3	954.1	957.7	964.5	966.3	964.0	964.5	964.9
25°	889.1	916.7	934.7	939.2	938.8	934.2	929.3	920.7	919.8	916.2	909.0
27.5°	893.6	904.0	901.8	883.3	864.8	863.0	833.2	817.0	798.5	801.2	790.8
30°	869.3	855.8	823.7	776.8	757.4	725.8	692.5	657.7	644.2	629.3	656.8
32.5°	809.7	761.5	704.6	643.7	611.3	583.3	547.6	522.4	507.9	495.8	519.2
35°	720.0	644.6	569.3	511.6	484.9	459.7	426.3	413.7	395.6	397.4	399.7
37.5°	604.5	521.5	464.6	407.8	390.2	379.8	355.5	336.1	329.8	328.0	328.0
40°	496.2	428.1	377.6	332.9	319.4	310.8	291.4	282.4	275.6	273.8	276.1
42.5°	410.5	352.3	313.1	283.3	273.8	263.0	254.9	243.6	242.2	239.1	243.1
45°	344.6	294.1	264.8	243.1	235.0	231.0	221.9	215.2	212.5	212.0	215.2
47.5°	292.3	253.1	227.4	213.8	207.5	203.5	195.8	193.1	190.4	191.3	189.9
50°	245.4	216.1	199.4	187.2	183.2	179.1	174.1	171.4	170.1	170.1	169.6
52.5°	210.7	186.3	175.5	164.2	162.4	160.1	154.7	152.9	150.7	150.2	152.0
55°	180.4	163.8	152.9	146.2	144.4	139.8	137.6	135.3	134.0	133.1	133.5
57.5°	154.3	141.6	134.4	128.6	125.4	123.6	119.5	119.1	118.2	118.2	117.7
60°	132.6	123.6	115.0	111.4	109.2	106.9	106.5	103.8	102.4	103.3	102.9
62.5°	112.3	105.1	100.1	96.1	94.7	92.9	91.6	90.7	89.3	89.8	89.8
65°	93.8	88.0	84.4	80.7	80.3	78.5	78.0	77.1	77.1	76.7	77.6
67.5°	77.1	73.1	69.9	67.7	66.3	66.8	65.0	63.6	63.6	63.2	64.5
70°	61.4	59.1	55.9	53.2	51.4	51.4	49.2	48.7	48.7	48.7	48.3
72.5°	47.4	43.3	42.0	41.1	41.1	41.1	40.1	40.1	39.7	40.1	39.7
75°	35.2	34.7	33.8	33.4	33.4	32.9	32.5	32.5	32.5	32.5	32.5
77.5°	27.5	27.5	26.6	26.2	26.2	26.2	25.7	25.7	25.3	25.3	25.3
80°	20.3	20.3	19.4	19.4	19.4	18.9	18.9	18.9	19.4	18.9	18.9
82.5°	14.0	14.0	13.5	14.0	13.5	13.1	13.1	13.1	12.6	13.1	13.1
85°	8.1	8.1	7.7	7.2	7.7	7.7	7.2	7.7	7.2	7.7	7.2
87.5°	3.2	2.7	2.7	2.7	2.3	2.7	2.3	2.3	2.7	2.3	2.7
90°	23.6	24.6	25.5	26.5	27.5	28.5	27.5	28.5	29.5	28.5	29.5
92.5°	136.6	97.3	75.7	65.8	62.4	59.0	57.0	53.1	54.0	52.1	54.0
95°	472.6	353.7	239.8	187.7	170.0	152.3	133.6	124.8	117.9	114.0	117.9
97.5°	926.6	812.6	613.2	483.4	427.4	371.4	305.6	268.3	244.7	233.9	244.7
100°	1124.1	1158.5	1078.9	963.9	894.2	824.4	725.2	653.4	615.1	616.1	615.1
102.5°	1133.9	1273.5	1290.2	1235.1	1197.3	1159.5	1087.8	1034.7	1004.2	975.7	1004.2
105°	1072.0	1277.4	1375.7	1394.3	1381.6	1368.8	1323.6	1286.2	1254.8	1249.9	1254.8
107.5°	983.6	1218.4	1372.7	1449.4	1462.6	1475.9	1470.0	1452.3	1439.5	1428.7	1439.5
110°	901.1	1126.1	1306.9	1430.7	1465.1	1499.5	1527.0	1534.8	1532.9	1530.9	1532.9

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	829.3	1034.7	1220.4	1362.9	1409.6	1456.2	1512.2	1540.7	1550.6	1551.5	1550.6
115°	774.3	956.1	1127.1	1271.5	1325.0	1378.6	1452.3	1495.5	1515.2	1520.1	1515.2
117.5°	737.9	895.2	1046.5	1179.1	1234.6	1290.2	1366.8	1415.0	1444.4	1451.3	1444.4
120°	710.4	849.0	981.6	1099.5	1149.2	1198.8	1276.4	1331.4	1355.0	1360.9	1355.0
122.5°	687.8	812.6	929.6	1036.7	1081.9	1127.1	1193.9	1242.0	1268.6	1276.4	1268.6
125°	669.2	781.2	888.3	982.6	1021.9	1061.2	1124.1	1167.3	1191.9	1198.8	1191.9
127.5°	651.5	752.7	850.0	936.4	972.8	1009.1	1066.1	1103.5	1126.1	1132.0	1126.1
130°	637.7	726.2	814.6	894.2	927.6	961.0	1013.1	1048.4	1069.1	1076.9	1069.1
132.5°	624.9	701.6	781.2	853.9	885.4	916.8	964.9	1000.3	1018.0	1022.9	1018.0
135°	614.1	680.0	749.7	813.6	841.6	869.6	917.8	947.2	964.9	971.8	964.9
137.5°	604.3	659.3	718.3	775.3	800.3	825.4	866.7	897.1	911.9	917.8	911.9
140°	595.5	641.6	691.8	738.9	760.0	781.2	818.5	846.0	861.8	860.8	861.8
142.5°	587.6	624.9	666.2	705.5	723.2	740.9	771.4	794.9	808.7	807.7	808.7
145°	580.7	612.2	644.6	676.0	690.2	704.5	729.1	749.7	757.6	759.6	757.6
147.5°	573.8	601.4	627.9	654.4	664.8	675.1	694.7	709.4	717.3	718.3	717.3
150°	567.0	589.6	612.2	632.8	642.2	651.5	666.2	677.0	682.9	682.9	682.9
152.5°	559.1	578.8	597.4	615.1	622.5	629.9	640.7	650.5	653.4	653.4	653.4
155°	551.2	568.0	583.7	598.4	604.3	610.2	619.0	626.9	628.9	629.9	628.9
157.5°	542.4	556.2	569.9	581.7	586.6	591.5	599.4	605.3	607.3	607.3	607.3
160°	533.6	546.3	557.1	567.0	570.4	573.8	580.7	586.6	586.6	585.6	586.6
162.5°	524.7	534.5	543.4	552.2	555.2	558.1	562.1	567.0	567.0	566.0	567.0
165°	516.9	524.7	530.6	537.5	540.0	542.4	546.3	550.3	549.3	549.3	549.3
167.5°	509.0	515.9	520.8	524.7	526.7	528.6	530.6	533.6	532.6	532.6	532.6
170°	502.1	507.0	510.0	513.9	514.9	515.9	516.9	518.8	517.8	517.8	517.8
172.5°	495.2	499.2	501.1	504.1	504.6	505.1	505.1	507.0	505.1	504.1	505.1
175°	490.3	492.3	493.3	495.2	495.2	495.2	495.2	496.2	495.2	494.3	495.2
177.5°	486.4	487.4	488.4	489.3	489.3	489.3	488.4	489.3	487.4	487.4	487.4
180°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	568.8	566.1	564.3	563.0	561.6	565.7	560.3	554.4	550.4	547.6	546.7
5°	628.4	622.5	617.6	613.5	614.4	614.4	604.9	594.6	585.5	580.6	575.2
7.5°	697.4	691.1	681.2	678.9	677.1	665.8	656.4	637.4	626.1	614.9	604.9
10°	766.0	757.9	748.4	745.2	740.7	726.7	712.3	687.9	674.0	653.2	640.1
12.5°	830.0	820.1	810.6	808.4	801.6	789.4	764.6	739.4	715.5	693.4	670.3
15°	883.7	881.0	866.6	857.6	842.7	826.0	820.6	786.3	756.1	733.1	691.6
17.5°	928.8	916.2	902.7	896.8	890.9	871.5	852.1	817.0	784.5	750.6	724.0
20°	964.9	950.9	941.5	932.9	930.2	908.1	877.4	846.3	810.6	772.8	738.0
22.5°	966.7	964.9	958.6	953.6	948.2	933.8	909.4	870.6	832.7	791.2	745.7
25°	929.3	926.6	944.6	940.1	943.7	938.3	925.2	892.7	848.5	799.8	753.8
27.5°	816.5	844.0	872.4	882.4	889.1	908.5	914.9	896.8	861.2	809.3	757.9
30°	663.1	699.7	745.7	770.5	789.4	825.5	872.4	878.3	861.6	820.1	757.0
32.5°	520.6	554.0	591.0	620.3	645.5	719.5	782.7	828.2	836.4	814.7	759.2
35°	419.5	434.0	469.2	497.1	531.4	594.6	669.0	742.5	792.1	794.9	752.5
37.5°	346.0	353.7	384.3	400.1	420.4	475.9	545.4	641.5	718.6	755.2	733.5
40°	286.5	304.0	321.6	330.7	345.1	383.4	450.2	525.5	621.2	688.8	704.2
42.5°	248.6	256.2	267.5	280.1	289.2	322.5	367.2	436.2	522.4	616.7	659.1
45°	219.2	221.9	233.7	241.8	251.3	274.7	306.3	364.0	439.8	532.8	604.9
47.5°	194.9	200.3	206.6	211.6	217.9	235.9	263.0	305.0	371.7	454.7	532.3
50°	173.2	176.4	184.5	186.8	191.3	203.9	224.7	256.7	311.7	378.0	458.3
52.5°	152.9	158.8	161.9	165.1	169.2	179.5	193.1	219.2	260.7	323.0	391.1
55°	137.1	138.9	143.5	146.2	149.3	156.5	168.3	187.7	220.1	269.8	334.3
57.5°	121.8	121.8	126.3	128.6	131.7	137.1	147.5	162.4	185.9	222.8	281.9
60°	105.6	106.0	109.6	112.3	113.2	118.6	127.2	138.9	157.0	184.1	232.3
62.5°	91.1	93.4	95.2	96.1	99.2	102.4	109.6	117.7	130.4	154.3	188.6
65°	78.9	79.4	80.7	81.7	83.0	86.6	92.0	97.4	108.3	125.9	153.8
67.5°	65.0	66.8	68.6	68.6	69.9	71.7	77.1	81.7	89.8	100.1	119.1
70°	48.7	49.6	52.3	53.7	55.5	58.6	61.4	64.1	70.4	78.0	92.5
72.5°	40.6	40.6	41.5	42.0	42.0	44.2	48.3	51.0	54.1	59.5	69.5
75°	32.5	32.5	33.8	33.4	34.3	35.2	35.6	37.4	39.2	43.3	49.2
77.5°	25.7	26.2	26.2	26.6	26.6	27.1	27.5	28.4	29.3	31.6	34.3
80°	18.9	19.4	19.4	19.8	19.8	20.3	20.8	21.2	22.1	23.0	24.4
82.5°	13.1	13.5	13.5	14.0	13.5	14.0	14.4	14.4	14.9	15.8	16.2
85°	7.7	7.7	8.1	7.7	7.7	7.7	8.1	8.1	8.6	9.9	9.9
87.5°	2.3	2.7	2.3	2.7	2.7	2.7	2.7	3.2	3.2	3.6	4.1
90°	28.5	27.5	28.5	27.5	26.5	25.5	24.6	23.6	24.6	21.6	18.7
92.5°	53.1	57.0	59.0	62.4	65.8	75.7	97.3	136.6	182.8	202.4	151.3
95°	124.8	133.6	152.3	170.0	187.7	239.8	353.7	472.6	582.7	518.8	357.7
97.5°	268.3	305.6	371.4	427.4	483.4	613.2	812.6	926.6	896.1	669.2	398.0
100°	653.4	725.2	824.4	894.2	963.9	1078.9	1158.5	1124.1	930.5	628.9	370.4
102.5°	1034.7	1087.8	1159.5	1197.3	1235.1	1290.2	1273.5	1133.9	866.7	569.9	346.9
105°	1286.2	1323.6	1368.8	1381.6	1394.3	1375.7	1277.4	1072.0	790.0	523.7	338.0
107.5°	1452.3	1470.0	1475.9	1462.6	1449.4	1372.7	1218.4	983.6	722.2	490.3	336.1
110°	1534.8	1527.0	1499.5	1465.1	1430.7	1306.9	1126.1	901.1	666.2	472.6	341.0

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1540.7	1512.2	1456.2	1409.6	1362.9	1220.4	1034.7	829.3	628.9	462.8	350.8
115°	1495.5	1452.3	1378.6	1325.0	1271.5	1127.1	956.1	774.3	604.3	461.8	361.6
117.5°	1415.0	1366.8	1290.2	1234.6	1179.1	1046.5	895.2	737.9	587.6	462.8	375.4
120°	1331.4	1276.4	1198.8	1149.2	1099.5	981.6	849.0	710.4	576.8	466.7	391.1
122.5°	1242.0	1193.9	1127.1	1081.9	1036.7	929.6	812.6	687.8	569.9	473.6	405.8
125°	1167.3	1124.1	1061.2	1021.9	982.6	888.3	781.2	669.2	564.0	480.5	421.5
127.5°	1103.5	1066.1	1009.1	972.8	936.4	850.0	752.7	651.5	561.1	488.4	434.3
130°	1048.4	1013.1	961.0	927.6	894.2	814.6	726.2	637.7	558.1	496.2	447.1
132.5°	1000.3	964.9	916.8	885.4	853.9	781.2	701.6	624.9	557.1	502.1	458.9
135°	947.2	917.8	869.6	841.6	813.6	749.7	680.0	614.1	556.2	508.0	468.7
137.5°	897.1	866.7	825.4	800.3	775.3	718.3	659.3	604.3	554.2	511.9	476.6
140°	846.0	818.5	781.2	760.0	738.9	691.8	641.6	595.5	553.2	515.9	482.5
142.5°	794.9	771.4	740.9	723.2	705.5	666.2	624.9	587.6	551.2	518.8	488.4
145°	749.7	729.1	704.5	690.2	676.0	644.6	612.2	580.7	549.3	519.8	492.3
147.5°	709.4	694.7	675.1	664.8	654.4	627.9	601.4	573.8	546.3	519.8	495.2
150°	677.0	666.2	651.5	642.2	632.8	612.2	589.6	567.0	542.4	519.8	496.2
152.5°	650.5	640.7	629.9	622.5	615.1	597.4	578.8	559.1	537.5	516.9	498.2
155°	626.9	619.0	610.2	604.3	598.4	583.7	568.0	551.2	531.6	514.9	498.2
157.5°	605.3	599.4	591.5	586.6	581.7	569.9	556.2	542.4	526.7	511.9	499.2
160°	586.6	580.7	573.8	570.4	567.0	557.1	546.3	533.6	520.8	510.0	499.2
162.5°	567.0	562.1	558.1	555.2	552.2	543.4	534.5	524.7	514.9	506.0	498.2
165°	550.3	546.3	542.4	540.0	537.5	530.6	524.7	516.9	509.0	502.1	496.2
167.5°	533.6	530.6	528.6	526.7	524.7	520.8	515.9	509.0	503.1	498.2	495.2
170°	518.8	516.9	515.9	514.9	513.9	510.0	507.0	502.1	497.2	494.3	492.3
172.5°	507.0	505.1	505.1	504.6	504.1	501.1	499.2	495.2	492.3	491.3	491.3
175°	496.2	495.2	495.2	495.2	495.2	493.3	492.3	490.3	488.4	488.4	489.3
177.5°	489.3	488.4	489.3	489.3	489.3	488.4	487.4	486.4	485.4	486.4	488.4
180°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	545.4	543.1	540.9	540.9	535.9	531.4	529.2	530.1	527.3	523.7	520.1
5°	569.3	560.3	558.5	553.5	546.7	537.3	532.3	527.8	522.4	515.2	508.4
7.5°	591.4	579.7	573.4	568.4	555.3	542.2	531.4	524.2	514.7	503.9	495.8
10°	620.3	598.6	591.9	580.6	562.1	543.6	531.0	519.2	506.1	493.5	482.7
12.5°	643.3	618.5	605.8	594.6	570.7	547.2	526.0	511.6	495.8	481.8	467.8
15°	669.4	641.5	619.4	605.8	575.6	547.2	523.3	503.0	485.4	468.3	456.1
17.5°	682.1	646.9	637.0	617.6	573.8	545.4	516.1	494.4	473.2	453.4	438.9
20°	701.9	660.9	636.1	623.0	584.2	542.2	507.9	483.1	461.0	439.8	424.5
22.5°	703.3	658.6	642.4	617.6	569.8	532.8	500.7	470.5	444.8	424.9	409.2
25°	700.1	654.6	632.0	612.2	572.5	527.3	486.3	456.5	431.3	408.3	389.8
27.5°	698.8	642.8	621.6	601.8	557.1	511.6	477.7	443.9	415.0	394.7	375.8
30°	697.0	630.2	604.5	581.5	540.4	499.4	458.8	429.5	401.9	376.2	357.3
32.5°	685.2	613.1	586.9	562.5	518.3	477.3	445.2	414.1	384.3	360.4	343.3
35°	681.6	597.3	563.0	536.8	493.5	457.0	423.1	397.4	369.5	345.5	325.2
37.5°	671.3	581.0	544.0	510.7	465.5	430.8	406.0	380.3	353.2	327.5	311.3
40°	653.2	562.1	520.1	485.8	439.4	404.2	381.2	362.2	335.6	312.6	292.8
42.5°	626.6	542.7	497.6	461.5	410.1	377.1	358.2	340.1	317.6	293.7	277.4
45°	595.9	517.0	475.0	434.9	382.5	350.5	330.7	319.8	299.1	278.8	259.8
47.5°	554.0	490.4	448.9	407.4	354.1	323.0	307.2	296.4	281.9	259.8	244.5
50°	501.2	456.1	416.8	379.8	326.2	296.4	280.6	272.5	260.3	244.5	229.6
52.5°	442.5	416.4	383.9	349.6	297.7	269.8	255.3	249.0	240.0	225.1	212.5
55°	383.4	372.2	350.1	316.2	268.0	245.0	232.3	224.2	217.4	206.6	195.8
57.5°	330.7	325.2	309.9	283.7	243.1	219.2	208.4	203.0	197.6	189.5	178.6
60°	276.1	281.9	266.2	253.1	216.1	195.3	185.9	180.0	177.3	170.1	163.3
62.5°	228.7	234.1	225.1	215.2	189.0	170.5	164.7	159.2	157.4	151.1	144.4
65°	185.9	192.6	185.9	180.4	164.7	149.3	142.1	139.4	137.6	133.5	128.1
67.5°	148.0	154.7	151.6	144.8	139.8	127.2	123.2	120.4	119.5	116.4	111.9
70°	111.4	120.9	121.8	117.7	113.2	107.4	104.7	103.8	101.5	98.8	96.1
72.5°	80.3	91.1	91.6	91.6	88.9	88.9	86.2	84.8	84.8	82.1	78.9
75°	59.1	66.3	67.2	68.1	69.5	70.8	69.0	69.0	68.6	65.9	64.5
77.5°	39.2	45.6	47.8	51.0	52.8	52.8	53.7	54.6	53.7	52.3	51.4
80°	25.3	29.8	32.5	34.3	37.0	38.3	39.7	40.1	39.2	38.8	37.4
82.5°	16.7	18.0	19.4	21.7	24.8	27.1	27.1	26.6	27.5	27.1	26.6
85°	9.5	10.4	10.8	11.3	13.1	15.3	15.8	16.2	17.1	16.2	15.3
87.5°	3.6	4.1	4.1	4.1	5.0	5.4	6.8	8.6	8.1	7.2	7.2
90°	15.7	12.8	11.8	10.8	8.8	5.9	3.9	2.0	3.9	5.9	8.8
92.5°	99.2	67.8	59.0	50.1	40.3	31.4	21.6	14.7	21.6	31.4	40.3
95°	211.3	127.7	108.6	89.4	63.9	47.2	36.4	33.4	36.4	47.2	63.9
97.5°	228.0	145.4	124.3	103.2	77.6	62.9	54.0	53.1	54.0	62.9	77.6
100°	225.0	156.2	137.0	117.9	94.3	80.6	73.7	72.7	73.7	80.6	94.3
102.5°	228.9	169.0	151.8	134.6	114.0	101.2	95.3	93.3	95.3	101.2	114.0
105°	236.8	183.7	168.5	153.3	134.6	122.8	116.9	114.0	116.9	122.8	134.6
107.5°	249.6	202.4	188.2	173.9	156.2	144.4	138.5	135.6	138.5	144.4	156.2
110°	266.3	222.1	208.4	194.6	177.9	167.0	162.1	159.2	162.1	167.0	177.9

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	283.0	242.7	229.4	216.2	199.5	188.7	183.7	180.8	183.7	188.7	199.5
115°	301.7	264.3	251.0	237.8	221.1	211.3	205.4	201.4	205.4	211.3	221.1
117.5°	321.3	284.0	271.7	259.4	240.7	231.9	227.0	222.1	227.0	231.9	240.7
120°	340.0	304.6	292.3	280.0	261.4	251.5	246.6	243.7	246.6	251.5	261.4
122.5°	359.6	325.2	312.0	298.7	281.0	270.2	265.3	262.4	265.3	270.2	281.0
125°	378.3	343.9	330.6	317.4	298.7	287.9	282.0	280.0	282.0	287.9	298.7
127.5°	395.0	361.6	348.4	335.1	314.4	303.6	296.7	293.8	296.7	303.6	314.4
130°	409.7	377.3	364.0	350.8	330.2	318.4	309.5	306.6	309.5	318.4	330.2
132.5°	422.5	391.1	378.3	365.5	344.9	330.2	320.3	316.4	320.3	330.2	344.9
135°	435.3	404.8	391.6	378.3	357.7	342.9	332.1	328.2	332.1	342.9	357.7
137.5°	444.1	414.7	402.4	390.1	369.5	353.7	342.9	339.0	342.9	353.7	369.5
140°	453.0	424.5	412.2	399.9	380.3	364.5	354.7	349.8	354.7	364.5	380.3
142.5°	459.9	432.4	421.0	409.7	390.1	376.3	365.5	361.6	365.5	376.3	390.1
145°	465.8	440.2	428.9	417.6	400.9	386.2	377.3	374.4	377.3	386.2	400.9
147.5°	470.7	447.1	437.2	427.4	410.7	398.0	389.1	387.1	389.1	398.0	410.7
150°	475.6	453.0	444.2	435.3	421.5	408.8	400.9	399.9	400.9	408.8	421.5
152.5°	478.5	459.9	451.6	443.2	431.4	420.6	412.7	412.7	412.7	420.6	431.4
155°	482.5	465.8	458.9	452.0	441.2	431.4	425.5	425.5	425.5	431.4	441.2
157.5°	484.4	470.7	465.3	459.9	450.0	441.2	436.3	435.3	436.3	441.2	450.0
160°	487.4	475.6	470.7	465.8	458.9	451.0	447.1	447.1	447.1	451.0	458.9
162.5°	488.4	478.5	474.6	470.7	464.8	458.9	455.9	455.9	455.9	458.9	464.8
165°	489.3	481.5	478.0	474.6	470.7	465.8	463.8	464.8	463.8	465.8	470.7
167.5°	489.3	483.4	481.0	478.5	475.6	471.7	470.7	471.7	470.7	471.7	475.6
170°	488.4	483.4	482.4	481.5	479.5	476.6	475.6	477.6	475.6	476.6	479.5
172.5°	488.4	484.4	483.9	483.4	482.5	480.5	480.5	481.5	480.5	480.5	482.5
175°	487.4	485.4	484.9	484.4	484.4	482.5	483.4	484.4	483.4	482.5	484.4
177.5°	486.4	485.4	485.4	485.4	485.4	484.4	485.4	486.4	485.4	484.4	485.4
180°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	520.1	517.9	517.0	514.7	509.3	505.7	501.6	498.9	499.4	497.1	498.5
5°	503.9	503.4	500.3	495.8	488.1	484.0	476.8	473.2	471.4	471.9	469.2
7.5°	490.4	486.3	484.0	476.8	469.6	461.0	455.2	452.0	449.3	446.6	444.8
10°	475.0	471.4	467.8	460.1	450.2	442.1	434.0	430.8	426.7	424.9	423.6
12.5°	458.8	456.5	452.0	443.0	431.7	424.0	414.6	412.8	407.4	403.7	402.8
15°	443.9	442.5	434.4	424.0	412.8	405.1	397.0	391.6	382.5	384.3	381.2
17.5°	428.1	422.2	417.3	403.3	397.9	386.1	376.7	374.0	367.7	363.6	359.5
20°	410.5	406.9	400.6	391.6	378.5	364.9	357.7	353.2	349.6	343.3	341.5
22.5°	393.8	389.3	383.9	372.2	360.9	349.6	339.7	335.6	331.1	326.6	323.9
25°	380.7	374.0	368.1	353.7	342.4	332.9	326.6	319.8	313.5	310.8	309.9
27.5°	360.4	356.4	350.5	337.0	326.6	316.2	310.4	305.9	299.1	295.9	293.2
30°	347.4	339.2	332.5	321.6	311.3	300.0	294.6	289.2	285.1	281.0	277.9
32.5°	329.8	323.4	318.0	307.2	296.8	286.5	280.6	272.5	270.2	267.1	263.4
35°	312.6	308.6	302.7	291.0	279.7	272.5	266.2	258.5	255.8	253.5	250.4
37.5°	296.4	290.5	286.5	275.2	265.3	256.7	251.7	245.4	243.6	240.9	238.6
40°	282.4	276.5	272.5	261.2	250.8	241.8	238.6	232.3	229.6	226.5	225.1
42.5°	266.6	261.6	256.2	248.1	237.3	228.3	221.9	218.3	214.7	213.4	210.7
45°	249.9	245.4	241.3	232.3	221.0	214.7	209.3	204.4	201.6	199.4	197.6
47.5°	235.5	231.4	226.0	216.1	207.1	201.2	195.8	190.8	188.1	185.4	183.2
50°	218.8	216.5	210.7	201.2	192.6	185.9	180.9	176.4	174.6	171.4	167.8
52.5°	203.9	199.8	194.9	187.2	179.5	171.4	164.7	161.9	158.8	157.0	153.8
55°	186.3	183.6	178.2	171.4	163.3	156.5	151.6	148.0	143.9	142.1	138.0
57.5°	171.4	166.5	163.8	155.2	147.5	140.7	137.1	133.5	129.0	126.3	124.5
60°	155.2	150.7	146.6	139.4	134.0	126.8	121.3	118.2	115.0	111.4	109.6
62.5°	139.4	135.8	130.8	125.0	118.2	112.3	108.3	103.8	102.0	98.3	97.0
65°	122.3	119.5	115.5	108.7	103.3	98.3	94.3	90.7	88.9	87.5	86.6
67.5°	106.9	103.3	100.6	94.7	88.9	84.8	82.6	80.3	78.0	76.7	75.3
70°	91.1	88.4	85.7	80.3	76.2	72.6	70.8	69.0	67.7	66.3	65.0
72.5°	74.9	73.5	70.8	67.2	64.1	61.4	60.0	57.7	56.4	54.1	53.2
75°	61.8	59.5	58.2	55.0	52.3	50.1	48.3	45.6	43.8	42.9	42.4
77.5°	48.7	47.8	46.0	43.3	42.0	39.7	37.0	36.1	35.2	35.2	34.7
80°	36.5	35.2	33.8	31.6	30.2	28.4	28.4	28.4	28.0	28.4	28.0
82.5°	24.8	23.9	23.0	21.7	21.2	21.2	21.7	21.7	21.7	21.7	21.7
85°	14.4	14.4	14.4	14.9	14.4	14.4	14.9	15.3	14.9	14.9	14.4
87.5°	6.8	6.8	7.2	7.2	7.7	7.7	7.7	7.7	7.7	7.7	8.1
90°	10.8	11.8	12.8	15.7	18.7	21.6	24.6	23.6	24.6	25.5	26.5
92.5°	50.1	59.0	67.8	99.2	151.3	202.4	182.8	136.6	97.3	75.7	65.8
95°	89.4	108.6	127.7	211.3	357.7	518.8	582.7	472.6	353.7	239.8	187.7
97.5°	103.2	124.3	145.4	228.0	398.0	669.2	896.1	926.6	812.6	613.2	483.4
100°	117.9	137.0	156.2	225.0	370.4	628.9	930.5	1124.1	1158.5	1078.9	963.9
102.5°	134.6	151.8	169.0	228.9	346.9	569.9	866.7	1133.9	1273.5	1290.2	1235.1
105°	153.3	168.5	183.7	236.8	338.0	523.7	790.0	1072.0	1277.4	1375.7	1394.3
107.5°	173.9	188.2	202.4	249.6	336.1	490.3	722.2	983.6	1218.4	1372.7	1449.4
110°	194.6	208.4	222.1	266.3	341.0	472.6	666.2	901.1	1126.1	1306.9	1430.7

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	216.2	229.4	242.7	283.0	350.8	462.8	628.9	829.3	1034.7	1220.4	1362.9
115°	237.8	251.0	264.3	301.7	361.6	461.8	604.3	774.3	956.1	1127.1	1271.5
117.5°	259.4	271.7	284.0	321.3	375.4	462.8	587.6	737.9	895.2	1046.5	1179.1
120°	280.0	292.3	304.6	340.0	391.1	466.7	576.8	710.4	849.0	981.6	1099.5
122.5°	298.7	312.0	325.2	359.6	405.8	473.6	569.9	687.8	812.6	929.6	1036.7
125°	317.4	330.6	343.9	378.3	421.5	480.5	564.0	669.2	781.2	888.3	982.6
127.5°	335.1	348.4	361.6	395.0	434.3	488.4	561.1	651.5	752.7	850.0	936.4
130°	350.8	364.0	377.3	409.7	447.1	496.2	558.1	637.7	726.2	814.6	894.2
132.5°	365.5	378.3	391.1	422.5	458.9	502.1	557.1	624.9	701.6	781.2	853.9
135°	378.3	391.6	404.8	435.3	468.7	508.0	556.2	614.1	680.0	749.7	813.6
137.5°	390.1	402.4	414.7	444.1	476.6	511.9	554.2	604.3	659.3	718.3	775.3
140°	399.9	412.2	424.5	453.0	482.5	515.9	553.2	595.5	641.6	691.8	738.9
142.5°	409.7	421.0	432.4	459.9	488.4	518.8	551.2	587.6	624.9	666.2	705.5
145°	417.6	428.9	440.2	465.8	492.3	519.8	549.3	580.7	612.2	644.6	676.0
147.5°	427.4	437.2	447.1	470.7	495.2	519.8	546.3	573.8	601.4	627.9	654.4
150°	435.3	444.2	453.0	475.6	496.2	519.8	542.4	567.0	589.6	612.2	632.8
152.5°	443.2	451.6	459.9	478.5	498.2	516.9	537.5	559.1	578.8	597.4	615.1
155°	452.0	458.9	465.8	482.5	498.2	514.9	531.6	551.2	568.0	583.7	598.4
157.5°	459.9	465.3	470.7	484.4	499.2	511.9	526.7	542.4	556.2	569.9	581.7
160°	465.8	470.7	475.6	487.4	499.2	510.0	520.8	533.6	546.3	557.1	567.0
162.5°	470.7	474.6	478.5	488.4	498.2	506.0	514.9	524.7	534.5	543.4	552.2
165°	474.6	478.0	481.5	489.3	496.2	502.1	509.0	516.9	524.7	530.6	537.5
167.5°	478.5	481.0	483.4	489.3	495.2	498.2	503.1	509.0	515.9	520.8	524.7
170°	481.5	482.4	483.4	488.4	492.3	494.3	497.2	502.1	507.0	510.0	513.9
172.5°	483.4	483.9	484.4	488.4	491.3	491.3	492.3	495.2	499.2	501.1	504.1
175°	484.4	484.9	485.4	487.4	489.3	488.4	488.4	490.3	492.3	493.3	495.2
177.5°	485.4	485.4	485.4	486.4	488.4	486.4	485.4	486.4	487.4	488.4	489.3
180°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	498.0	498.5	497.1	494.4	494.0	494.9	497.6	496.7	494.4	498.5	494.9
5°	470.5	468.3	467.3	468.3	465.5	464.2	466.9	465.5	466.9	467.3	468.7
7.5°	443.9	444.3	441.6	442.1	438.5	439.4	439.4	439.4	440.7	441.6	443.4
10°	420.9	421.8	418.6	419.1	416.4	414.6	415.9	418.6	418.6	418.6	419.5
12.5°	402.4	398.3	396.1	395.6	392.5	391.6	394.3	395.2	397.4	397.4	398.8
15°	379.4	378.5	376.7	376.7	369.0	370.8	371.7	374.9	379.4	375.8	376.7
17.5°	358.6	356.4	354.1	353.2	352.3	349.6	353.2	352.8	355.5	355.9	357.3
20°	340.1	338.3	333.8	334.3	335.2	331.1	333.4	333.4	336.1	338.8	341.9
22.5°	322.1	320.3	318.0	318.9	316.2	315.3	315.3	317.6	320.7	323.0	322.5
25°	308.1	305.0	303.6	302.2	300.9	301.8	300.4	302.7	305.0	306.3	305.0
27.5°	292.3	291.0	288.3	286.9	284.7	285.6	286.5	288.3	289.6	289.6	291.0
30°	277.0	275.2	274.3	272.9	272.9	271.1	271.6	273.4	274.7	276.1	277.9
32.5°	262.1	260.7	259.4	259.4	258.5	258.0	257.6	260.3	260.3	263.0	263.0
35°	249.9	247.7	247.7	245.4	246.3	245.9	245.0	246.8	247.2	249.0	248.6
37.5°	236.4	236.4	235.5	233.2	231.4	231.9	234.1	234.1	235.5	235.0	236.4
40°	222.8	221.9	221.9	220.6	220.1	219.7	220.1	220.6	222.8	222.4	222.8
42.5°	209.3	209.8	207.5	207.5	207.5	206.2	206.6	207.1	208.0	208.9	210.2
45°	196.2	195.3	194.9	194.0	193.1	193.5	193.1	194.9	194.4	195.3	196.7
47.5°	182.2	180.9	180.4	178.6	178.6	179.5	179.1	180.4	180.9	182.2	181.3
50°	168.7	166.9	165.6	166.0	163.3	164.2	164.2	165.6	166.9	167.4	168.3
52.5°	152.9	152.5	152.0	149.8	149.3	148.9	149.3	149.8	151.6	152.9	153.4
55°	137.6	137.1	134.4	133.5	132.2	132.2	133.1	133.5	136.7	137.1	138.9
57.5°	123.6	122.3	119.1	118.6	118.6	118.6	117.3	119.1	120.0	122.3	122.3
60°	108.3	108.3	105.6	105.6	106.0	105.6	105.6	106.0	106.0	107.8	108.7
62.5°	96.1	95.6	95.6	94.7	94.3	94.7	94.3	94.3	94.7	96.1	97.4
65°	85.3	84.8	84.4	83.9	83.0	83.0	83.5	84.4	84.4	85.3	85.7
67.5°	74.9	74.9	74.0	74.0	73.5	73.1	73.5	73.1	74.9	74.9	75.3
70°	64.5	64.1	62.7	62.3	60.9	61.4	61.4	62.7	63.2	64.1	65.0
72.5°	51.9	51.9	51.0	50.1	50.5	49.6	49.6	50.1	50.1	51.4	51.9
75°	42.9	42.0	41.5	42.0	41.5	42.4	41.5	41.5	42.4	42.4	42.4
77.5°	35.2	35.2	34.7	34.7	35.2	34.7	35.2	35.2	35.2	34.7	35.2
80°	28.9	28.4	28.4	28.4	28.0	28.0	28.0	28.0	28.0	28.0	28.0
82.5°	21.7	21.7	21.2	21.7	21.7	21.2	21.7	21.2	21.2	21.7	21.7
85°	14.4	15.3	14.4	14.4	14.9	14.9	15.3	14.9	15.3	14.4	14.9
87.5°	7.7	8.1	8.1	7.7	7.7	8.1	8.1	8.1	8.6	7.7	8.1
90°	27.5	28.5	27.5	28.5	29.5	28.5	29.5	28.5	27.5	28.5	27.5
92.5°	62.4	59.0	57.0	53.1	54.0	52.1	54.0	53.1	57.0	59.0	62.4
95°	170.0	152.3	133.6	124.8	117.9	114.0	117.9	124.8	133.6	152.3	170.0
97.5°	427.4	371.4	305.6	268.3	244.7	233.9	244.7	268.3	305.6	371.4	427.4
100°	894.2	824.4	725.2	653.4	615.1	616.1	615.1	653.4	725.2	824.4	894.2
102.5°	1197.3	1159.5	1087.8	1034.7	1004.2	975.7	1004.2	1034.7	1087.8	1159.5	1197.3
105°	1381.6	1368.8	1323.6	1286.2	1254.8	1249.9	1254.8	1286.2	1323.6	1368.8	1381.6
107.5°	1462.6	1475.9	1470.0	1452.3	1439.5	1428.7	1439.5	1452.3	1470.0	1475.9	1462.6
110°	1465.1	1499.5	1527.0	1534.8	1532.9	1530.9	1532.9	1534.8	1527.0	1499.5	1465.1

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1409.6	1456.2	1512.2	1540.7	1550.6	1551.5	1550.6	1540.7	1512.2	1456.2	1409.6
115°	1325.0	1378.6	1452.3	1495.5	1515.2	1520.1	1515.2	1495.5	1452.3	1378.6	1325.0
117.5°	1234.6	1290.2	1366.8	1415.0	1444.4	1451.3	1444.4	1415.0	1366.8	1290.2	1234.6
120°	1149.2	1198.8	1276.4	1331.4	1355.0	1360.9	1355.0	1331.4	1276.4	1198.8	1149.2
122.5°	1081.9	1127.1	1193.9	1242.0	1268.6	1276.4	1268.6	1242.0	1193.9	1127.1	1081.9
125°	1021.9	1061.2	1124.1	1167.3	1191.9	1198.8	1191.9	1167.3	1124.1	1061.2	1021.9
127.5°	972.8	1009.1	1066.1	1103.5	1126.1	1132.0	1126.1	1103.5	1066.1	1009.1	972.8
130°	927.6	961.0	1013.1	1048.4	1069.1	1076.9	1069.1	1048.4	1013.1	961.0	927.6
132.5°	885.4	916.8	964.9	1000.3	1018.0	1022.9	1018.0	1000.3	964.9	916.8	885.4
135°	841.6	869.6	917.8	947.2	964.9	971.8	964.9	947.2	917.8	869.6	841.6
137.5°	800.3	825.4	866.7	897.1	911.9	917.8	911.9	897.1	866.7	825.4	800.3
140°	760.0	781.2	818.5	846.0	861.8	860.8	861.8	846.0	818.5	781.2	760.0
142.5°	723.2	740.9	771.4	794.9	808.7	807.7	808.7	794.9	771.4	740.9	723.2
145°	690.2	704.5	729.1	749.7	757.6	759.6	757.6	749.7	729.1	704.5	690.2
147.5°	664.8	675.1	694.7	709.4	717.3	718.3	717.3	709.4	694.7	675.1	664.8
150°	642.2	651.5	666.2	677.0	682.9	682.9	682.9	677.0	666.2	651.5	642.2
152.5°	622.5	629.9	640.7	650.5	653.4	653.4	653.4	650.5	640.7	629.9	622.5
155°	604.3	610.2	619.0	626.9	628.9	629.9	628.9	626.9	619.0	610.2	604.3
157.5°	586.6	591.5	599.4	605.3	607.3	607.3	607.3	605.3	599.4	591.5	586.6
160°	570.4	573.8	580.7	586.6	586.6	585.6	586.6	586.6	580.7	573.8	570.4
162.5°	555.2	558.1	562.1	567.0	567.0	566.0	567.0	567.0	562.1	558.1	555.2
165°	540.0	542.4	546.3	550.3	549.3	549.3	549.3	550.3	546.3	542.4	540.0
167.5°	526.7	528.6	530.6	533.6	532.6	532.6	532.6	533.6	530.6	528.6	526.7
170°	514.9	515.9	516.9	518.8	517.8	517.8	517.8	518.8	516.9	515.9	514.9
172.5°	504.6	505.1	505.1	507.0	505.1	504.1	505.1	507.0	505.1	505.1	504.6
175°	495.2	495.2	495.2	496.2	495.2	494.3	495.2	496.2	495.2	495.2	495.2
177.5°	489.3	489.3	488.4	489.3	487.4	487.4	487.4	489.3	488.4	489.3	489.3
180°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	498.5	500.3	498.5	494.9	498.5	500.7	503.0	506.6	508.4	508.4	511.1
5°	470.1	473.7	472.3	471.4	475.0	477.3	480.9	485.4	490.4	493.5	497.1
7.5°	444.8	447.0	449.3	449.3	452.9	457.9	463.3	468.7	475.0	479.5	482.2
10°	422.7	424.5	425.8	427.7	433.1	438.5	445.7	452.5	457.9	462.8	467.3
12.5°	401.5	404.2	407.4	408.7	412.8	419.5	426.3	434.4	443.0	448.0	452.5
15°	381.2	382.5	386.1	390.2	393.8	401.0	409.6	418.2	425.4	433.1	437.1
17.5°	360.4	360.9	370.4	368.1	379.8	386.6	391.1	399.2	411.0	417.3	423.6
20°	340.1	344.6	348.7	351.0	357.3	364.9	378.0	384.3	393.8	399.7	405.1
22.5°	324.3	331.1	331.1	336.5	339.7	346.9	356.4	368.6	378.9	383.0	390.7
25°	310.4	313.5	318.9	320.7	326.6	332.9	339.2	352.3	363.6	369.0	374.4
27.5°	292.3	296.4	303.6	303.6	311.3	318.0	325.7	334.3	345.5	353.2	359.1
30°	278.3	282.4	285.6	290.5	293.7	300.0	313.5	319.8	329.8	336.5	343.7
32.5°	265.3	268.4	271.1	276.5	280.1	287.4	294.6	305.9	314.4	320.7	328.4
35°	250.8	254.0	257.6	261.6	267.1	273.8	280.6	290.1	298.6	304.5	310.8
37.5°	237.3	239.5	245.0	247.7	252.2	258.5	267.1	277.0	284.7	289.2	295.5
40°	224.2	226.0	230.1	235.0	238.2	243.1	252.2	260.7	270.2	275.6	280.6
42.5°	210.2	212.5	216.1	221.0	226.0	231.4	236.4	246.3	254.9	259.4	264.8
45°	198.0	199.4	202.1	207.1	212.0	216.1	223.8	232.8	240.9	244.5	250.4
47.5°	183.6	185.0	189.0	191.3	196.7	202.1	209.8	218.8	226.0	229.6	235.0
50°	168.7	170.1	172.8	177.7	181.3	187.2	194.0	201.6	210.7	215.6	218.8
52.5°	154.3	157.0	159.2	163.3	167.8	173.7	180.0	187.2	194.9	199.8	203.5
55°	139.8	142.1	144.8	147.1	152.5	157.9	165.1	171.9	178.6	183.2	187.2
57.5°	123.6	126.8	129.5	134.0	138.0	142.6	150.7	156.1	164.2	167.4	171.0
60°	109.6	112.8	115.0	118.6	122.3	128.1	133.5	140.3	147.1	151.1	155.6
62.5°	97.9	99.2	100.6	104.2	107.8	113.2	118.6	125.4	132.6	134.9	138.5
65°	86.2	87.5	89.8	92.9	95.6	98.8	104.7	110.1	116.8	120.4	121.8
67.5°	76.2	77.6	78.0	80.3	82.6	86.2	89.3	94.7	101.0	103.3	106.0
70°	65.0	67.2	67.7	69.5	70.4	72.6	76.2	80.3	85.3	89.3	91.6
72.5°	51.9	55.0	55.9	58.6	60.0	62.3	65.0	68.1	71.3	73.1	74.9
75°	42.4	43.3	43.8	46.0	48.3	51.4	52.8	54.6	57.3	59.5	61.4
77.5°	35.2	35.6	36.1	36.1	36.5	38.3	41.1	43.3	45.1	46.0	47.4
80°	28.4	28.0	28.0	28.4	28.4	28.4	29.3	32.5	33.4	35.6	35.2
82.5°	22.1	21.2	21.7	21.2	21.2	21.2	21.2	21.7	21.7	23.0	23.9
85°	14.4	14.9	14.4	14.4	14.0	14.4	14.0	14.0	13.5	13.5	13.1
87.5°	7.7	8.1	7.7	7.7	7.2	7.7	7.2	7.2	6.8	6.8	5.9
90°	26.5	25.5	24.6	23.6	24.6	21.6	18.7	15.7	12.8	11.8	10.8
92.5°	65.8	75.7	97.3	136.6	182.8	202.4	151.3	99.2	67.8	59.0	50.1
95°	187.7	239.8	353.7	472.6	582.7	518.8	357.7	211.3	127.7	108.6	89.4
97.5°	483.4	613.2	812.6	926.6	896.1	669.2	398.0	228.0	145.4	124.3	103.2
100°	963.9	1078.9	1158.5	1124.1	930.5	628.9	370.4	225.0	156.2	137.0	117.9
102.5°	1235.1	1290.2	1273.5	1133.9	866.7	569.9	346.9	228.9	169.0	151.8	134.6
105°	1394.3	1375.7	1277.4	1072.0	790.0	523.7	338.0	236.8	183.7	168.5	153.3
107.5°	1449.4	1372.7	1218.4	983.6	722.2	490.3	336.1	249.6	202.4	188.2	173.9
110°	1430.7	1306.9	1126.1	901.1	666.2	472.6	341.0	266.3	222.1	208.4	194.6

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1362.9	1220.4	1034.7	829.3	628.9	462.8	350.8	283.0	242.7	229.4	216.2
115°	1271.5	1127.1	956.1	774.3	604.3	461.8	361.6	301.7	264.3	251.0	237.8
117.5°	1179.1	1046.5	895.2	737.9	587.6	462.8	375.4	321.3	284.0	271.7	259.4
120°	1099.5	981.6	849.0	710.4	576.8	466.7	391.1	340.0	304.6	292.3	280.0
122.5°	1036.7	929.6	812.6	687.8	569.9	473.6	405.8	359.6	325.2	312.0	298.7
125°	982.6	888.3	781.2	669.2	564.0	480.5	421.5	378.3	343.9	330.6	317.4
127.5°	936.4	850.0	752.7	651.5	561.1	488.4	434.3	395.0	361.6	348.4	335.1
130°	894.2	814.6	726.2	637.7	558.1	496.2	447.1	409.7	377.3	364.0	350.8
132.5°	853.9	781.2	701.6	624.9	557.1	502.1	458.9	422.5	391.1	378.3	365.5
135°	813.6	749.7	680.0	614.1	556.2	508.0	468.7	435.3	404.8	391.6	378.3
137.5°	775.3	718.3	659.3	604.3	554.2	511.9	476.6	444.1	414.7	402.4	390.1
140°	738.9	691.8	641.6	595.5	553.2	515.9	482.5	453.0	424.5	412.2	399.9
142.5°	705.5	666.2	624.9	587.6	551.2	518.8	488.4	459.9	432.4	421.0	409.7
145°	676.0	644.6	612.2	580.7	549.3	519.8	492.3	465.8	440.2	428.9	417.6
147.5°	654.4	627.9	601.4	573.8	546.3	519.8	495.2	470.7	447.1	437.2	427.4
150°	632.8	612.2	589.6	567.0	542.4	519.8	496.2	475.6	453.0	444.2	435.3
152.5°	615.1	597.4	578.8	559.1	537.5	516.9	498.2	478.5	459.9	451.6	443.2
155°	598.4	583.7	568.0	551.2	531.6	514.9	498.2	482.5	465.8	458.9	452.0
157.5°	581.7	569.9	556.2	542.4	526.7	511.9	499.2	484.4	470.7	465.3	459.9
160°	567.0	557.1	546.3	533.6	520.8	510.0	499.2	487.4	475.6	470.7	465.8
162.5°	552.2	543.4	534.5	524.7	514.9	506.0	498.2	488.4	478.5	474.6	470.7
165°	537.5	530.6	524.7	516.9	509.0	502.1	496.2	489.3	481.5	478.0	474.6
167.5°	524.7	520.8	515.9	509.0	503.1	498.2	495.2	489.3	483.4	481.0	478.5
170°	513.9	510.0	507.0	502.1	497.2	494.3	492.3	488.4	483.4	482.4	481.5
172.5°	504.1	501.1	499.2	495.2	492.3	491.3	491.3	488.4	484.4	483.9	483.4
175°	495.2	493.3	492.3	490.3	488.4	488.4	489.3	487.4	485.4	484.9	484.4
177.5°	489.3	488.4	487.4	486.4	485.4	486.4	488.4	486.4	485.4	485.4	485.4
180°	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4	485.4

TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	526.9	526.9	526.9	526.9
2.5°	513.4	516.5	522.8	528.2
5°	502.5	507.5	517.0	526.4
7.5°	489.5	497.1	509.3	522.4
10°	476.8	486.7	501.6	517.0
12.5°	464.2	474.6	490.4	510.2
15°	449.3	460.1	479.1	503.0
17.5°	436.2	450.7	467.8	491.7
20°	422.2	433.1	455.2	480.4
22.5°	404.6	422.7	443.4	470.1
25°	390.7	406.4	427.2	457.4
27.5°	373.5	392.0	417.3	443.9
30°	359.5	374.9	398.3	430.4
32.5°	343.3	361.3	385.7	417.3
35°	328.9	344.2	367.2	399.2
37.5°	311.7	328.4	354.1	382.5
40°	296.8	313.1	337.4	364.0
42.5°	278.8	295.9	320.3	342.8
45°	264.4	280.1	299.5	320.3
47.5°	246.8	263.4	282.4	296.8
50°	231.0	246.3	261.2	273.4
52.5°	213.8	227.8	241.3	250.4
55°	198.0	208.9	219.7	226.0
57.5°	179.5	189.9	198.9	202.5
60°	163.3	171.9	177.7	181.8
62.5°	146.2	152.5	157.0	159.2
65°	129.5	134.0	136.2	138.5
67.5°	112.3	116.4	117.7	120.4
70°	94.3	98.8	99.7	101.0
72.5°	80.7	80.7	82.6	84.4
75°	64.5	65.4	66.3	66.3
77.5°	50.5	50.5	51.4	51.9
80°	37.0	37.4	37.4	37.0
82.5°	25.3	26.2	25.3	24.8
85°	14.0	15.8	14.9	14.9
87.5°	5.9	5.9	6.8	5.9
90°	8.8	5.9	3.9	2.0
92.5°	40.3	31.4	21.6	14.7
95°	63.9	47.2	36.4	33.4
97.5°	77.6	62.9	54.0	53.1
100°	94.3	80.6	73.7	72.7
102.5°	114.0	101.2	95.3	93.3
105°	134.6	122.8	116.9	114.0
107.5°	156.2	144.4	138.5	135.6
110°	177.9	167.0	162.1	159.2



TEST NUMBER: P1012426

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	199.5	188.7	183.7	180.8
115°	221.1	211.3	205.4	201.4
117.5°	240.7	231.9	227.0	222.1
120°	261.4	251.5	246.6	243.7
122.5°	281.0	270.2	265.3	262.4
125°	298.7	287.9	282.0	280.0
127.5°	314.4	303.6	296.7	293.8
130°	330.2	318.4	309.5	306.6
132.5°	344.9	330.2	320.3	316.4
135°	357.7	342.9	332.1	328.2
137.5°	369.5	353.7	342.9	339.0
140°	380.3	364.5	354.7	349.8
142.5°	390.1	376.3	365.5	361.6
145°	400.9	386.2	377.3	374.4
147.5°	410.7	398.0	389.1	387.1
150°	421.5	408.8	400.9	399.9
152.5°	431.4	420.6	412.7	412.7
155°	441.2	431.4	425.5	425.5
157.5°	450.0	441.2	436.3	435.3
160°	458.9	451.0	447.1	447.1
162.5°	464.8	458.9	455.9	455.9
165°	470.7	465.8	463.8	464.8
167.5°	475.6	471.7	470.7	471.7
170°	479.5	476.6	475.6	477.6
172.5°	482.5	480.5	480.5	481.5
175°	484.4	482.5	483.4	484.4
177.5°	485.4	484.4	485.4	486.4
180°	485.4	485.4	485.4	485.4

(END OF REPORT)