

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012432

Luminaire Tested: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012432
REPORT IS A COMBINATION OF REPORTS P993155 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4801.0 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	102	102	102	102		91	91	91	91		70	70	70		52	52	52		35	35	35
1	93	89	85	82		83	79	76	74		62	60	58		46	45	43		31	30	30
2	85	78	72	67		75	70	65	61		55	51	49		41	38	37		28	26	25
3	77	69	62	56		69	62	56	51		48	44	41		36	34	31		25	23	22
4	71	61	53	48		63	55	48	43		43	39	35		32	29	27		22	21	19
5	65	54	47	41		58	49	42	37		39	34	30		29	26	24		20	18	17
6	60	49	41	35		53	44	37	32		35	30	26		26	23	21		18	16	15
7	55	44	36	31		49	39	33	28		31	27	23		24	21	18		17	15	13
8	51	40	32	27		46	36	29	25		29	24	21		22	19	16		15	13	12
9	48	36	29	24		43	33	26	22		26	22	18		20	17	15		14	12	11
10	44	33	26	22		40	30	24	20		24	20	16		18	15	13		13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5481	5481	5481	5481
5°	5486	6313	5500	4683
10°	5437	7621	5461	4091
15°	5381	8649	5381	3607
20°	5270	9329	5300	3200
25°	5190	8864	5180	2920
30°	5096	6141	5086	2645
35°	4982	3943	4960	2439
40°	4842	2784	4818	2233
45°	4596	2228	4591	2033
50°	4296	1864	4282	1800
55°	3957	1536	3926	1525
60°	3625	1269	3590	1297
65°	3234	1016	3256	1100
70°	2877	706	2954	889
75°	2438	524	2537	684
80°	1944	347	2106	512
85°	1383	164	1508	319

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7318 cd/sqm

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.0
10°-20°	156.5	3.3
20°-30°	246.6	5.1
30°-40°	256.4	5.3
40°-50°	219.3	4.6
50°-60°	167.2	3.5
60°-70°	107.1	2.2
70°-80°	51.3	1.1
80°-90°	16.1	0.3
90°-100°	254.7	5.3
100°-110°	745.6	15.5
110°-120°	728.1	15.2
120°-130°	579.9	12.1
130°-140°	457.5	9.5
140°-150°	341.3	7.1
150°-160°	238.0	5.0
160°-170°	139.8	2.9
170°-180°	45.5	0.9
0°-30°	453.1	9.4
0°-40°	709.5	14.8
0°-60°	1096.0	22.8
0°-90°	1270.6	26.5
90°-120°	1728.5	36.0
90°-150°	3107.2	64.7
90°-180°	3530.0	73.5
0°-180°	4801.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	509	605	510	449	509	48
15°	486	859	486	358	486	137
25°	442	886	441	292	442	204
35°	386	384	384	238	386	241
45°	310	205	309	187	310	238
55°	218	129	217	128	218	196
65°	134	74	135	80	134	134
75°	64	31	67	41	64	69
85°	14	7	16	14	14	16
90°	2	28	2	28	2	3
95°	32	110	32	110	32	34
105°	110	1208	110	1208	110	117
115°	195	1470	195	1470	195	193
125°	271	1159	271	1159	271	241
135°	317	940	317	940	317	245
145°	362	734	362	734	362	227
155°	411	609	411	609	411	189
165°	449	531	449	531	449	127
175°	468	478	468	478	468	44
180°	469	469	469	469	469	

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	510.5	514.0	516.6	518.4	522.7	525.4	527.5	531.5	531.5	532.3	534.1
5°	508.8	516.2	521.4	528.4	537.6	541.9	548.0	553.3	560.7	564.6	568.5
7.5°	504.9	515.3	526.2	536.7	550.2	558.9	565.0	578.5	588.1	599.9	609.1
10°	499.6	514.0	528.0	544.1	562.4	575.5	584.7	602.5	620.8	637.4	651.4
12.5°	493.1	510.5	530.6	550.2	575.9	589.0	603.8	626.1	652.2	673.2	691.9
15°	486.1	506.2	528.8	552.8	585.1	603.4	624.8	651.8	681.0	711.1	736.8
17.5°	475.2	500.5	525.8	560.7	598.6	609.5	627.8	664.9	701.1	728.1	759.5
20°	464.3	492.7	524.5	555.9	596.9	622.1	639.1	678.4	717.2	749.9	780.0
22.5°	454.3	483.9	517.1	556.7	595.1	620.4	641.8	682.7	727.7	764.3	801.3
25°	442.1	474.3	511.0	548.5	595.1	614.3	637.8	685.4	732.9	775.2	821.0
27.5°	429.0	461.7	497.9	536.3	579.0	607.3	630.4	681.4	739.4	784.8	831.9
30°	415.9	449.5	484.4	518.8	566.8	593.8	620.4	676.6	742.9	794.8	831.0
32.5°	403.3	431.6	466.1	499.6	547.2	576.8	606.9	671.8	744.2	787.8	805.3
35°	385.8	415.5	443.4	479.1	527.1	556.3	591.6	671.4	738.6	765.6	756.9
37.5°	369.7	394.6	421.2	453.0	502.2	540.2	576.8	660.1	719.8	721.5	672.3
40°	351.8	372.3	394.6	428.1	481.3	518.8	558.5	642.6	685.8	660.1	573.3
42.5°	331.3	349.7	367.1	399.8	457.8	499.6	542.4	620.8	636.5	577.2	487.0
45°	309.5	324.4	340.5	374.9	432.9	474.3	517.1	587.3	571.1	487.4	401.5
47.5°	286.9	299.5	315.2	346.6	406.3	448.6	489.2	539.3	498.3	408.5	336.6
50°	264.2	274.2	289.5	321.8	379.3	417.7	455.2	487.9	430.3	350.5	278.2
52.5°	242.0	249.8	265.5	293.0	348.8	385.4	412.4	425.1	366.7	289.5	241.5
55°	218.4	227.1	237.6	265.5	320.9	347.9	365.8	365.4	305.2	245.5	199.7
57.5°	195.8	203.6	212.8	240.7	285.6	303.9	319.1	311.7	254.6	201.0	171.3
60°	175.7	180.1	190.1	213.6	247.6	263.3	272.1	259.4	208.0	169.6	141.7
62.5°	153.9	158.3	166.5	188.8	209.7	218.0	225.4	209.3	171.8	138.2	121.2
65°	133.8	139.5	144.7	162.6	174.0	184.0	183.1	169.6	134.3	112.5	98.5
67.5°	116.4	118.6	122.9	133.8	139.1	146.5	146.9	131.7	108.1	91.6	83.3
70°	97.7	99.8	102.9	108.1	111.6	113.4	112.5	99.0	81.5	71.5	64.1
72.5°	81.5	81.1	83.3	83.3	86.8	86.3	83.7	73.2	61.9	53.6	49.3
75°	64.1	64.5	65.0	64.1	62.8	61.0	58.9	51.0	43.6	39.7	35.8
77.5°	50.1	49.3	49.7	46.6	44.9	43.2	40.1	36.2	30.1	29.2	27.5
80°	35.8	35.3	34.9	33.6	29.6	27.9	25.7	23.5	22.2	21.4	20.9
82.5°	24.0	24.0	23.1	20.5	18.3	17.0	16.6	15.7	14.4	14.4	14.0
85°	14.4	14.0	13.1	10.5	9.2	9.2	9.2	9.2	8.3	8.3	7.8
87.5°	5.7	5.2	3.9	3.9	3.5	3.5	3.5	3.1	3.1	2.6	2.6
90°	1.9	3.8	5.7	8.6	10.5	11.4	12.4	15.2	18.1	20.9	23.8
92.5°	14.3	20.9	30.4	39.0	48.5	57.0	65.6	96.0	146.3	195.7	176.7
95°	32.3	35.2	45.6	61.8	86.5	105.0	123.5	204.3	345.8	501.6	563.4
97.5°	51.3	52.3	60.8	75.1	99.8	120.2	140.6	220.4	384.8	647.0	866.5
100°	70.3	71.3	77.9	91.2	114.0	132.6	151.1	217.6	358.2	608.0	899.7
102.5°	90.3	92.2	97.9	110.2	130.2	146.8	163.4	221.4	335.4	551.0	838.0
105°	110.2	113.1	118.8	130.2	148.2	163.0	177.7	229.0	326.8	506.4	763.9
107.5°	131.1	134.0	139.7	151.1	168.2	182.0	195.7	241.3	324.9	474.1	698.3
110°	153.9	156.8	161.5	172.0	188.1	201.4	214.7	257.5	329.7	457.0	644.2

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	174.8	177.7	182.4	192.9	209.0	221.8	234.7	273.6	339.2	447.5	608.0
115°	194.8	198.6	204.3	213.8	229.9	242.8	255.6	291.7	349.6	446.5	584.3
117.5°	214.7	219.5	224.2	232.8	250.8	262.7	274.6	310.7	362.9	447.5	568.1
120°	235.6	238.5	243.2	252.7	270.8	282.6	294.5	328.7	378.1	451.3	557.7
122.5°	253.7	256.5	261.3	271.7	288.8	301.6	314.5	347.7	392.4	457.9	551.0
125°	270.8	272.7	278.4	288.8	306.9	319.7	332.5	365.8	407.6	464.6	545.3
127.5°	284.1	286.9	293.6	304.0	324.0	336.8	349.6	381.9	419.9	472.2	542.5
130°	296.4	299.3	307.8	319.2	339.2	352.0	364.8	396.2	432.3	479.8	539.6
132.5°	305.9	309.7	319.2	333.5	353.4	365.8	378.1	408.5	443.7	485.5	538.7
135°	317.3	321.1	331.6	345.8	365.8	378.6	391.4	420.9	453.2	491.2	537.7
137.5°	327.8	331.6	342.0	357.2	377.2	389.0	400.9	429.4	460.8	495.0	535.8
140°	338.2	343.0	352.5	367.7	386.7	398.5	410.4	438.0	466.5	498.8	534.9
142.5°	349.6	353.4	363.9	377.2	396.2	407.1	418.0	444.6	472.2	501.6	533.0
145°	362.0	364.8	373.4	387.6	403.8	414.7	425.6	450.3	476.0	502.6	531.1
147.5°	374.3	376.2	384.8	397.1	413.3	422.8	432.3	455.1	478.8	502.6	528.2
150°	386.7	387.6	395.2	407.6	420.9	429.4	438.0	459.8	479.8	502.6	524.4
152.5°	399.0	399.0	406.6	417.1	428.5	436.6	444.6	462.7	481.7	499.7	519.7
155°	411.4	411.4	417.1	426.6	437.0	443.6	450.3	466.5	481.7	497.8	514.0
157.5°	420.9	421.8	426.6	435.1	444.6	449.8	455.1	468.4	482.6	495.0	509.2
160°	432.3	432.3	436.1	443.7	450.3	455.0	459.8	471.2	482.6	493.1	503.5
162.5°	440.8	440.8	443.7	449.4	455.1	458.9	462.7	472.2	481.7	489.3	497.8
165°	449.4	448.4	450.3	455.1	458.9	462.2	465.5	473.1	479.8	485.5	492.1
167.5°	456.0	455.1	456.0	459.8	462.7	465.0	467.4	473.1	478.8	481.7	486.4
170°	461.7	459.8	460.8	463.6	465.5	466.4	467.4	472.2	476.0	477.9	480.7
172.5°	465.5	464.6	464.6	466.5	467.4	467.9	468.4	472.2	475.0	475.0	476.0
175°	468.4	467.4	466.5	468.4	468.4	468.8	469.3	471.2	473.1	472.2	472.2
177.5°	470.3	469.3	468.4	469.3	469.3	469.3	469.3	470.3	472.2	470.3	469.3
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	537.6	537.6	541.5	545.4	543.2	544.5	549.3	547.6	551.1	550.6	552.0
5°	578.1	582.9	586.8	595.1	596.4	595.1	603.4	605.6	609.5	604.7	606.9
7.5°	623.9	633.9	643.5	655.7	659.6	660.5	664.9	671.0	676.2	666.6	671.4
10°	668.4	683.6	703.2	714.1	723.7	727.2	730.7	734.6	740.7	746.4	742.0
12.5°	716.3	738.6	757.3	776.9	788.7	787.4	797.4	800.0	804.8	806.1	807.9
15°	755.6	786.9	798.7	827.9	830.5	839.3	850.6	860.6	861.9	859.3	859.3
17.5°	793.0	820.1	841.0	864.6	869.3	876.8	891.1	895.9	897.7	897.2	897.2
20°	823.6	841.4	876.8	896.4	904.2	913.8	923.8	929.9	931.3	933.0	930.4
22.5°	843.6	870.7	899.4	915.6	922.1	925.6	932.1	933.9	931.7	932.1	932.6
25°	859.3	885.9	903.4	907.7	907.3	902.9	898.1	889.8	889.0	885.5	878.5
27.5°	863.7	873.7	871.5	853.7	835.8	834.0	805.3	789.6	771.7	774.3	764.3
30°	840.1	827.1	796.1	750.8	732.0	701.5	669.2	635.7	622.6	608.2	634.8
32.5°	782.6	735.9	681.0	622.1	590.8	563.7	529.3	504.9	490.9	479.1	501.8
35°	695.8	623.0	550.2	494.4	468.7	444.3	412.0	399.8	382.4	384.1	386.3
37.5°	584.2	504.0	449.1	394.1	377.1	367.1	343.6	324.8	318.7	317.0	317.0
40°	479.6	413.7	364.9	321.8	308.7	300.4	281.6	272.9	266.4	264.6	266.8
42.5°	396.7	340.5	302.6	273.8	264.6	254.2	246.3	235.4	234.1	231.1	235.0
45°	333.1	284.3	255.9	235.0	227.1	223.2	214.5	208.0	205.3	204.9	208.0
47.5°	282.5	244.6	219.7	206.7	200.6	196.6	189.2	186.6	184.0	184.9	183.5
50°	237.2	208.8	192.7	180.9	177.0	173.1	168.3	165.7	164.4	164.4	163.9
52.5°	203.6	180.1	169.6	158.7	157.0	154.8	149.5	147.8	145.6	145.2	146.9
55°	174.4	158.3	147.8	141.3	139.5	135.2	133.0	130.8	129.5	128.6	129.1
57.5°	149.1	136.9	129.9	124.3	121.2	119.5	115.5	115.1	114.2	114.2	113.8
60°	128.2	119.5	111.2	107.7	105.5	103.3	102.9	100.3	99.0	99.8	99.4
62.5°	108.6	101.6	96.8	92.9	91.6	89.8	88.5	87.6	86.3	86.8	86.8
65°	90.7	85.0	81.5	78.0	77.6	75.9	75.4	74.6	74.6	74.1	75.0
67.5°	74.6	70.6	67.6	65.4	64.1	64.5	62.8	61.5	61.5	61.0	62.3
70°	59.3	57.1	54.1	51.4	49.7	49.7	47.5	47.1	47.1	47.1	46.6
72.5°	45.8	41.9	40.5	39.7	39.7	39.7	38.8	38.8	38.4	38.8	38.4
75°	34.0	33.6	32.7	32.3	32.3	31.8	31.4	31.4	31.4	31.4	31.4
77.5°	26.6	26.6	25.7	25.3	25.3	25.3	24.9	24.9	24.4	24.4	24.4
80°	19.6	19.6	18.7	18.7	18.7	18.3	18.3	18.3	18.7	18.3	18.3
82.5°	13.5	13.5	13.1	13.5	13.1	12.6	12.6	12.6	12.2	12.6	12.6
85°	7.8	7.8	7.4	7.0	7.4	7.4	7.0	7.4	7.0	7.4	7.0
87.5°	3.1	2.6	2.6	2.6	2.2	2.6	2.2	2.2	2.6	2.2	2.6
90°	22.8	23.8	24.7	25.7	26.6	27.6	26.6	27.6	28.5	27.6	28.5
92.5°	132.1	94.1	73.2	63.7	60.4	57.0	55.1	51.3	52.3	50.4	52.3
95°	457.0	342.0	231.8	181.5	164.4	147.3	129.2	120.7	114.0	110.2	114.0
97.5°	895.9	785.7	592.8	467.4	413.2	359.1	295.5	259.4	236.6	226.1	236.6
100°	1086.9	1120.1	1043.2	932.0	864.6	797.1	701.2	631.8	594.7	595.7	594.7
102.5°	1096.4	1231.3	1247.4	1194.2	1157.6	1121.1	1051.7	1000.4	971.0	943.4	971.0
105°	1036.5	1235.1	1330.1	1348.2	1335.8	1323.5	1279.8	1243.6	1213.2	1208.5	1213.2
107.5°	951.0	1178.1	1327.3	1401.4	1414.2	1427.0	1421.3	1404.2	1391.9	1381.4	1391.9
110°	871.2	1088.8	1263.6	1383.3	1416.6	1449.8	1476.4	1484.0	1482.1	1480.2	1482.1

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	801.9	1000.4	1180.0	1317.8	1362.9	1408.0	1462.2	1489.7	1499.2	1500.2	1499.2
115°	748.7	924.4	1089.7	1229.4	1281.2	1333.0	1404.2	1446.0	1465.0	1469.8	1465.0
117.5°	713.5	865.5	1011.8	1140.1	1193.8	1247.4	1321.6	1368.1	1396.6	1403.3	1396.6
120°	686.9	820.9	949.1	1063.1	1111.1	1159.1	1234.1	1287.4	1310.2	1315.9	1310.2
122.5°	665.1	785.7	898.8	1002.3	1046.0	1089.7	1154.3	1200.9	1226.5	1234.1	1226.5
125°	647.0	755.3	858.9	950.1	988.1	1026.1	1086.9	1128.7	1152.4	1159.1	1152.4
127.5°	629.9	727.8	821.8	905.4	940.6	975.7	1030.8	1066.9	1088.8	1094.5	1088.8
130°	616.6	702.1	787.6	864.6	896.9	929.2	979.5	1013.7	1033.7	1041.3	1033.7
132.5°	604.2	678.4	755.3	825.6	856.0	886.4	933.0	967.2	984.3	989.0	984.3
135°	593.8	657.5	724.9	786.7	813.8	840.8	887.4	915.9	933.0	939.6	933.0
137.5°	584.3	637.5	694.5	749.6	773.8	798.1	838.0	867.4	881.7	887.4	881.7
140°	575.7	620.4	668.9	714.5	734.9	755.3	791.4	818.0	833.2	832.3	833.2
142.5°	568.1	604.2	644.2	682.2	699.3	716.4	745.8	768.6	781.9	781.0	781.9
145°	561.5	591.9	623.2	653.7	667.4	681.2	705.0	724.9	732.5	734.4	732.5
147.5°	554.8	581.4	607.1	632.8	642.8	652.7	671.7	686.0	693.6	694.5	693.6
150°	548.2	570.0	591.9	611.8	620.8	629.9	644.2	654.6	660.3	660.3	660.3
152.5°	540.6	559.6	577.6	594.7	601.8	609.0	619.4	628.9	631.8	631.8	631.8
155°	533.0	549.1	564.3	578.6	584.3	590.0	598.5	606.1	608.0	609.0	608.0
157.5°	524.4	537.7	551.0	562.4	567.2	571.9	579.5	585.2	587.1	587.1	587.1
160°	515.9	528.2	538.7	548.2	551.5	554.8	561.5	567.2	567.2	566.2	567.2
162.5°	507.3	516.8	525.4	533.9	536.8	539.6	543.4	548.2	548.2	547.2	548.2
165°	499.7	507.3	513.0	519.7	522.0	524.4	528.2	532.0	531.1	531.1	531.1
167.5°	492.1	498.8	503.5	507.3	509.2	511.1	513.0	515.9	514.9	514.9	514.9
170°	485.5	490.2	493.1	496.9	497.8	498.8	499.7	501.6	500.7	500.7	500.7
172.5°	478.8	482.6	484.5	487.4	487.8	488.3	488.3	490.2	488.3	487.4	488.3
175°	474.1	476.0	476.9	478.8	478.8	478.8	478.8	479.8	478.8	477.9	478.8
177.5°	470.3	471.2	472.2	473.1	473.1	473.1	472.2	473.1	471.2	471.2	471.2
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	549.8	547.2	545.4	544.1	542.8	546.7	541.5	535.8	531.9	529.3	528.4
5°	607.3	601.7	596.9	592.9	593.8	593.8	584.7	574.6	565.9	561.1	555.9
7.5°	674.0	667.9	658.3	656.2	654.4	643.5	634.4	616.0	605.1	594.2	584.7
10°	740.3	732.4	723.3	720.2	715.9	702.4	688.4	664.9	651.4	631.3	618.7
12.5°	802.2	792.6	783.5	781.3	774.7	763.0	739.0	714.6	691.5	670.1	647.9
15°	854.1	851.5	837.5	828.8	814.4	798.3	793.0	759.9	730.7	708.5	668.4
17.5°	897.7	885.5	872.4	866.7	861.1	842.3	823.6	789.6	758.2	725.5	699.7
20°	932.6	919.0	909.9	901.6	899.0	877.6	848.0	817.9	783.5	746.8	713.3
22.5°	934.3	932.6	926.5	921.7	916.4	902.5	878.9	841.4	804.8	764.7	720.7
25°	898.1	895.5	912.9	908.6	912.1	906.8	894.2	862.8	820.1	773.0	728.5
27.5°	789.1	815.7	843.2	852.8	859.3	878.1	884.2	866.7	832.3	782.1	732.4
30°	640.9	676.2	720.7	744.7	763.0	797.8	843.2	848.9	832.7	792.6	731.6
32.5°	503.1	535.4	571.1	599.5	623.9	695.4	756.4	800.5	808.3	787.4	733.8
35°	405.5	419.4	453.4	480.5	513.6	574.6	646.6	717.6	765.6	768.2	727.2
37.5°	334.4	341.8	371.5	386.7	406.3	460.0	527.1	620.0	694.5	729.8	708.9
40°	276.8	293.9	310.9	319.6	333.5	370.6	435.1	507.9	600.3	665.7	680.6
42.5°	240.2	247.6	258.5	270.7	279.5	311.7	354.9	421.6	504.9	596.0	637.0
45°	211.9	214.5	225.8	233.7	242.8	265.5	296.0	351.8	425.1	514.9	584.7
47.5°	188.3	193.6	199.7	204.5	210.6	228.0	254.2	294.7	359.2	439.5	514.5
50°	167.4	170.5	178.3	180.5	184.9	197.1	217.1	248.1	301.3	365.4	443.0
52.5°	147.8	153.5	156.5	159.6	163.5	173.5	186.6	211.9	252.0	312.2	378.0
55°	132.5	134.3	138.6	141.3	144.3	151.3	162.6	181.4	212.8	260.7	323.1
57.5°	117.7	117.7	122.1	124.3	127.3	132.5	142.6	157.0	179.6	215.4	272.5
60°	102.0	102.5	105.9	108.6	109.4	114.7	122.9	134.3	151.7	177.9	224.5
62.5°	88.1	90.2	92.0	92.9	95.9	99.0	105.9	113.8	126.0	149.1	182.2
65°	76.3	76.7	78.0	78.9	80.2	83.7	88.9	94.2	104.6	121.6	148.7
67.5°	62.8	64.5	66.3	66.3	67.6	69.3	74.6	78.9	86.8	96.8	115.1
70°	47.1	48.0	50.6	51.9	53.6	56.7	59.3	61.9	68.0	75.4	89.4
72.5°	39.2	39.2	40.1	40.5	40.5	42.7	46.6	49.3	52.3	57.5	67.1
75°	31.4	31.4	32.7	32.3	33.1	34.0	34.4	36.2	37.9	41.9	47.5
77.5°	24.9	25.3	25.3	25.7	25.7	26.2	26.6	27.5	28.3	30.5	33.1
80°	18.3	18.7	18.7	19.2	19.2	19.6	20.1	20.5	21.4	22.2	23.5
82.5°	12.6	13.1	13.1	13.5	13.1	13.5	14.0	14.0	14.4	15.3	15.7
85°	7.4	7.4	7.8	7.4	7.4	7.4	7.8	7.8	8.3	9.6	9.6
87.5°	2.2	2.6	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.5	3.9
90°	27.6	26.6	27.6	26.6	25.7	24.7	23.8	22.8	23.8	20.9	18.1
92.5°	51.3	55.1	57.0	60.4	63.7	73.2	94.1	132.1	176.7	195.7	146.3
95°	120.7	129.2	147.3	164.4	181.5	231.8	342.0	457.0	563.4	501.6	345.8
97.5°	259.4	295.5	359.1	413.2	467.4	592.8	785.7	895.9	866.5	647.0	384.8
100°	631.8	701.2	797.1	864.6	932.0	1043.2	1120.1	1086.9	899.7	608.0	358.2
102.5°	1000.4	1051.7	1121.1	1157.6	1194.2	1247.4	1231.3	1096.4	838.0	551.0	335.4
105°	1243.6	1279.8	1323.5	1335.8	1348.2	1330.1	1235.1	1036.5	763.9	506.4	326.8
107.5°	1404.2	1421.3	1427.0	1414.2	1401.4	1327.3	1178.1	951.0	698.3	474.1	324.9
110°	1484.0	1476.4	1449.8	1416.6	1383.3	1263.6	1088.8	871.2	644.2	457.0	329.7

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1489.7	1462.2	1408.0	1362.9	1317.8	1180.0	1000.4	801.9	608.0	447.5	339.2
115°	1446.0	1404.2	1333.0	1281.2	1229.4	1089.7	924.4	748.7	584.3	446.5	349.6
117.5°	1368.1	1321.6	1247.4	1193.8	1140.1	1011.8	865.5	713.5	568.1	447.5	362.9
120°	1287.4	1234.1	1159.1	1111.1	1063.1	949.1	820.9	686.9	557.7	451.3	378.1
122.5°	1200.9	1154.3	1089.7	1046.0	1002.3	898.8	785.7	665.1	551.0	457.9	392.4
125°	1128.7	1086.9	1026.1	988.1	950.1	858.9	755.3	647.0	545.3	464.6	407.6
127.5°	1066.9	1030.8	975.7	940.6	905.4	821.8	727.8	629.9	542.5	472.2	419.9
130°	1013.7	979.5	929.2	896.9	864.6	787.6	702.1	616.6	539.6	479.8	432.3
132.5°	967.2	933.0	886.4	856.0	825.6	755.3	678.4	604.2	538.7	485.5	443.7
135°	915.9	887.4	840.8	813.8	786.7	724.9	657.5	593.8	537.7	491.2	453.2
137.5°	867.4	838.0	798.1	773.8	749.6	694.5	637.5	584.3	535.8	495.0	460.8
140°	818.0	791.4	755.3	734.9	714.5	668.9	620.4	575.7	534.9	498.8	466.5
142.5°	768.6	745.8	716.4	699.3	682.2	644.2	604.2	568.1	533.0	501.6	472.2
145°	724.9	705.0	681.2	667.4	653.7	623.2	591.9	561.5	531.1	502.6	476.0
147.5°	686.0	671.7	652.7	642.8	632.8	607.1	581.4	554.8	528.2	502.6	478.8
150°	654.6	644.2	629.9	620.8	611.8	591.9	570.0	548.2	524.4	502.6	479.8
152.5°	628.9	619.4	609.0	601.8	594.7	577.6	559.6	540.6	519.7	499.7	481.7
155°	606.1	598.5	590.0	584.3	578.6	564.3	549.1	533.0	514.0	497.8	481.7
157.5°	585.2	579.5	571.9	567.2	562.4	551.0	537.7	524.4	509.2	495.0	482.6
160°	567.2	561.5	554.8	551.5	548.2	538.7	528.2	515.9	503.5	493.1	482.6
162.5°	548.2	543.4	539.6	536.8	533.9	525.4	516.8	507.3	497.8	489.3	481.7
165°	532.0	528.2	524.4	522.0	519.7	513.0	507.3	499.7	492.1	485.5	479.8
167.5°	515.9	513.0	511.1	509.2	507.3	503.5	498.8	492.1	486.4	481.7	478.8
170°	501.6	499.7	498.8	497.8	496.9	493.1	490.2	485.5	480.7	477.9	476.0
172.5°	490.2	488.3	488.3	487.8	487.4	484.5	482.6	478.8	476.0	475.0	475.0
175°	479.8	478.8	478.8	478.8	478.8	476.9	476.0	474.1	472.2	472.2	473.1
177.5°	473.1	472.2	473.1	473.1	473.1	472.2	471.2	470.3	469.3	470.3	472.2
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	527.1	524.9	522.7	522.7	517.9	513.6	511.4	512.3	509.7	506.2	502.7
5°	550.2	541.5	539.7	534.9	528.4	519.3	514.5	510.1	504.9	497.9	491.4
7.5°	571.6	560.2	554.1	549.3	536.7	524.0	513.6	506.6	497.5	487.0	479.1
10°	599.5	578.5	572.0	561.1	543.2	525.4	513.1	501.8	489.2	477.0	466.5
12.5°	621.7	597.7	585.5	574.6	551.5	528.8	508.4	494.4	479.1	465.6	452.1
15°	647.0	620.0	598.6	585.5	556.3	528.8	505.7	486.1	469.1	452.5	440.8
17.5°	659.2	625.2	615.6	596.9	554.6	527.1	498.8	477.8	457.3	438.2	424.2
20°	678.4	638.7	614.7	602.1	564.6	524.0	490.9	466.9	445.6	425.1	410.3
22.5°	679.7	636.5	620.8	596.9	550.6	514.9	483.9	454.7	429.9	410.7	395.4
25°	676.6	632.6	610.8	591.6	553.3	509.7	470.0	441.2	416.8	394.6	376.7
27.5°	675.3	621.3	600.8	581.6	538.4	494.4	461.7	429.0	401.1	381.5	363.2
30°	673.6	609.1	584.2	562.0	522.3	482.6	443.4	415.1	388.5	363.6	345.3
32.5°	662.3	592.5	567.2	543.7	500.9	461.3	430.3	400.2	371.5	348.3	331.8
35°	658.8	577.2	544.1	518.8	477.0	441.6	409.0	384.1	357.1	334.0	314.3
37.5°	648.7	561.5	525.8	493.5	449.9	416.4	392.4	367.5	341.4	316.5	300.8
40°	631.3	543.2	502.7	469.6	424.6	390.6	368.4	350.1	324.4	302.1	283.0
42.5°	605.6	524.5	480.9	446.0	396.3	364.5	346.2	328.7	306.9	283.8	268.1
45°	575.9	499.6	459.1	420.3	369.7	338.8	319.6	309.1	289.1	269.4	251.1
47.5°	535.4	473.9	433.8	393.7	342.2	312.2	296.9	286.4	272.5	251.1	236.3
50°	484.4	440.8	402.8	367.1	315.2	286.4	271.2	263.3	251.6	236.3	221.9
52.5°	427.7	402.4	371.0	337.9	287.7	260.7	246.8	240.7	231.9	217.6	205.3
55°	370.6	359.7	338.3	305.6	259.0	236.7	224.5	216.7	210.1	199.7	189.2
57.5°	319.6	314.3	299.5	274.2	235.0	211.9	201.4	196.2	191.0	183.1	172.6
60°	266.8	272.5	257.2	244.6	208.8	188.8	179.6	174.0	171.3	164.4	157.8
62.5°	221.0	226.3	217.6	208.0	182.7	164.8	159.1	153.9	152.2	146.1	139.5
65°	179.6	186.2	179.6	174.4	159.1	144.3	137.3	134.7	133.0	129.1	123.8
67.5°	143.0	149.5	146.5	139.9	135.2	122.9	119.0	116.4	115.5	112.5	108.1
70°	107.7	116.8	117.7	113.8	109.4	103.8	101.1	100.3	98.1	95.5	92.9
72.5°	77.6	88.1	88.5	88.5	85.9	85.9	83.3	82.0	82.0	79.3	76.3
75°	57.1	64.1	65.0	65.8	67.1	68.4	66.7	66.7	66.3	63.7	62.3
77.5°	37.9	44.0	46.2	49.3	51.0	51.0	51.9	52.8	51.9	50.6	49.7
80°	24.4	28.8	31.4	33.1	35.8	37.1	38.4	38.8	37.9	37.5	36.2
82.5°	16.1	17.4	18.7	20.9	24.0	26.2	26.2	25.7	26.6	26.2	25.7
85°	9.2	10.0	10.5	10.9	12.6	14.8	15.3	15.7	16.6	15.7	14.8
87.5°	3.5	3.9	3.9	3.9	4.8	5.2	6.5	8.3	7.8	7.0	7.0
90°	15.2	12.4	11.4	10.5	8.6	5.7	3.8	1.9	3.8	5.7	8.6
92.5°	96.0	65.6	57.0	48.5	39.0	30.4	20.9	14.3	20.9	30.4	39.0
95°	204.3	123.5	105.0	86.5	61.8	45.6	35.2	32.3	35.2	45.6	61.8
97.5°	220.4	140.6	120.2	99.8	75.1	60.8	52.3	51.3	52.3	60.8	75.1
100°	217.6	151.1	132.6	114.0	91.2	77.9	71.3	70.3	71.3	77.9	91.2
102.5°	221.4	163.4	146.8	130.2	110.2	97.9	92.2	90.3	92.2	97.9	110.2
105°	229.0	177.7	163.0	148.2	130.2	118.8	113.1	110.2	113.1	118.8	130.2
107.5°	241.3	195.7	182.0	168.2	151.1	139.7	134.0	131.1	134.0	139.7	151.1
110°	257.5	214.7	201.4	188.1	172.0	161.5	156.8	153.9	156.8	161.5	172.0

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	273.6	234.7	221.8	209.0	192.9	182.4	177.7	174.8	177.7	182.4	192.9
115°	291.7	255.6	242.8	229.9	213.8	204.3	198.6	194.8	198.6	204.3	213.8
117.5°	310.7	274.6	262.7	250.8	232.8	224.2	219.5	214.7	219.5	224.2	232.8
120°	328.7	294.5	282.6	270.8	252.7	243.2	238.5	235.6	238.5	243.2	252.7
122.5°	347.7	314.5	301.6	288.8	271.7	261.3	256.5	253.7	256.5	261.3	271.7
125°	365.8	332.5	319.7	306.9	288.8	278.4	272.7	270.8	272.7	278.4	288.8
127.5°	381.9	349.6	336.8	324.0	304.0	293.6	286.9	284.1	286.9	293.6	304.0
130°	396.2	364.8	352.0	339.2	319.2	307.8	299.3	296.4	299.3	307.8	319.2
132.5°	408.5	378.1	365.8	353.4	333.5	319.2	309.7	305.9	309.7	319.2	333.5
135°	420.9	391.4	378.6	365.8	345.8	331.6	321.1	317.3	321.1	331.6	345.8
137.5°	429.4	400.9	389.0	377.2	357.2	342.0	331.6	327.8	331.6	342.0	357.2
140°	438.0	410.4	398.5	386.7	367.7	352.5	343.0	338.2	343.0	352.5	367.7
142.5°	444.6	418.0	407.1	396.2	377.2	363.9	353.4	349.6	353.4	363.9	377.2
145°	450.3	425.6	414.7	403.8	387.6	373.4	364.8	362.0	364.8	373.4	387.6
147.5°	455.1	432.3	422.8	413.3	397.1	384.8	376.2	374.3	376.2	384.8	397.1
150°	459.8	438.0	429.4	420.9	407.6	395.2	387.6	386.7	387.6	395.2	407.6
152.5°	462.7	444.6	436.6	428.5	417.1	406.6	399.0	399.0	399.0	406.6	417.1
155°	466.5	450.3	443.6	437.0	426.6	417.1	411.4	411.4	411.4	417.1	426.6
157.5°	468.4	455.1	449.8	444.6	435.1	426.6	421.8	420.9	421.8	426.6	435.1
160°	471.2	459.8	455.0	450.3	443.7	436.1	432.3	432.3	432.3	436.1	443.7
162.5°	472.2	462.7	458.9	455.1	449.4	443.7	440.8	440.8	440.8	443.7	449.4
165°	473.1	465.5	462.2	458.9	455.1	450.3	448.4	449.4	448.4	450.3	455.1
167.5°	473.1	467.4	465.0	462.7	459.8	456.0	455.1	456.0	455.1	456.0	459.8
170°	472.2	467.4	466.4	465.5	463.6	460.8	459.8	461.7	459.8	460.8	463.6
172.5°	472.2	468.4	467.9	467.4	466.5	464.6	464.6	465.5	464.6	464.6	466.5
175°	471.2	469.3	468.8	468.4	468.4	466.5	467.4	468.4	467.4	466.5	468.4
177.5°	470.3	469.3	469.3	469.3	469.3	468.4	469.3	470.3	469.3	468.4	469.3
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	502.7	500.5	499.6	497.5	492.2	488.7	484.8	482.2	482.6	480.5	481.8
5°	487.0	486.6	483.5	479.1	471.7	467.8	460.8	457.3	455.6	456.0	453.4
7.5°	473.9	470.0	467.8	460.8	453.9	445.6	439.9	436.9	434.2	431.6	429.9
10°	459.1	455.6	452.1	444.7	435.1	427.3	419.4	416.4	412.4	410.7	409.4
12.5°	443.4	441.2	436.9	428.1	417.2	409.8	400.7	398.9	393.7	390.2	389.3
15°	429.0	427.7	419.8	409.8	398.9	391.5	383.7	378.4	369.7	371.5	368.4
17.5°	413.7	408.1	403.3	389.8	384.5	373.2	364.0	361.4	355.3	351.4	347.5
20°	396.7	393.3	387.2	378.4	365.8	352.7	345.7	341.4	337.9	331.8	330.0
22.5°	380.6	376.3	371.0	359.7	348.8	337.9	328.3	324.4	320.0	315.7	313.0
25°	368.0	361.4	355.8	341.8	330.9	321.8	315.7	309.1	303.0	300.4	299.5
27.5°	348.3	344.4	338.8	325.7	315.7	305.6	300.0	295.6	289.1	286.0	283.4
30°	335.7	327.9	321.3	310.9	300.8	289.9	284.7	279.5	275.5	271.6	268.6
32.5°	318.7	312.6	307.4	296.9	286.9	276.8	271.2	263.3	261.2	258.1	254.6
35°	302.1	298.2	292.5	281.2	270.3	263.3	257.2	249.8	247.2	245.0	242.0
37.5°	286.4	280.8	276.8	265.9	256.4	248.1	243.3	237.2	235.4	232.8	230.6
40°	272.9	267.3	263.3	252.4	242.4	233.7	230.6	224.5	221.9	218.9	217.6
42.5°	257.7	252.9	247.6	239.8	229.3	220.6	214.5	211.0	207.5	206.2	203.6
45°	241.5	237.2	233.2	224.5	213.6	207.5	202.3	197.5	194.9	192.7	191.0
47.5°	227.6	223.7	218.4	208.8	200.1	194.4	189.2	184.4	181.8	179.2	177.0
50°	211.5	209.3	203.6	194.4	186.2	179.6	174.8	170.5	168.7	165.7	162.2
52.5°	197.1	193.1	188.3	180.9	173.5	165.7	159.1	156.5	153.5	151.7	148.7
55°	180.1	177.4	172.2	165.7	157.8	151.3	146.5	143.0	139.1	137.3	133.4
57.5°	165.7	160.9	158.3	150.0	142.6	136.0	132.5	129.1	124.7	122.1	120.3
60°	150.0	145.6	141.7	134.7	129.5	122.5	117.3	114.2	111.2	107.7	105.9
62.5°	134.7	131.2	126.4	120.8	114.2	108.6	104.6	100.3	98.5	95.0	93.7
65°	118.2	115.5	111.6	105.1	99.8	95.0	91.1	87.6	85.9	84.6	83.7
67.5°	103.3	99.8	97.2	91.6	85.9	82.0	79.8	77.6	75.4	74.1	72.8
70°	88.1	85.5	82.8	77.6	73.7	70.2	68.4	66.7	65.4	64.1	62.8
72.5°	72.4	71.1	68.4	65.0	61.9	59.3	58.0	55.8	54.5	52.3	51.4
75°	59.7	57.5	56.2	53.2	50.6	48.4	46.6	44.0	42.3	41.4	41.0
77.5°	47.1	46.2	44.5	41.9	40.5	38.4	35.8	34.9	34.0	34.0	33.6
80°	35.3	34.0	32.7	30.5	29.2	27.5	27.5	27.5	27.0	27.5	27.0
82.5°	24.0	23.1	22.2	20.9	20.5	20.5	20.9	20.9	20.9	20.9	20.9
85°	14.0	14.0	14.0	14.4	14.0	14.0	14.4	14.8	14.4	14.4	14.0
87.5°	6.5	6.5	7.0	7.0	7.4	7.4	7.4	7.4	7.4	7.4	7.8
90°	10.5	11.4	12.4	15.2	18.1	20.9	23.8	22.8	23.8	24.7	25.7
92.5°	48.5	57.0	65.6	96.0	146.3	195.7	176.7	132.1	94.1	73.2	63.7
95°	86.5	105.0	123.5	204.3	345.8	501.6	563.4	457.0	342.0	231.8	181.5
97.5°	99.8	120.2	140.6	220.4	384.8	647.0	866.5	895.9	785.7	592.8	467.4
100°	114.0	132.6	151.1	217.6	358.2	608.0	899.7	1086.9	1120.1	1043.2	932.0
102.5°	130.2	146.8	163.4	221.4	335.4	551.0	838.0	1096.4	1231.3	1247.4	1194.2
105°	148.2	163.0	177.7	229.0	326.8	506.4	763.9	1036.5	1235.1	1330.1	1348.2
107.5°	168.2	182.0	195.7	241.3	324.9	474.1	698.3	951.0	1178.1	1327.3	1401.4
110°	188.1	201.4	214.7	257.5	329.7	457.0	644.2	871.2	1088.8	1263.6	1383.3

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	209.0	221.8	234.7	273.6	339.2	447.5	608.0	801.9	1000.4	1180.0	1317.8
115°	229.9	242.8	255.6	291.7	349.6	446.5	584.3	748.7	924.4	1089.7	1229.4
117.5°	250.8	262.7	274.6	310.7	362.9	447.5	568.1	713.5	865.5	1011.8	1140.1
120°	270.8	282.6	294.5	328.7	378.1	451.3	557.7	686.9	820.9	949.1	1063.1
122.5°	288.8	301.6	314.5	347.7	392.4	457.9	551.0	665.1	785.7	898.8	1002.3
125°	306.9	319.7	332.5	365.8	407.6	464.6	545.3	647.0	755.3	858.9	950.1
127.5°	324.0	336.8	349.6	381.9	419.9	472.2	542.5	629.9	727.8	821.8	905.4
130°	339.2	352.0	364.8	396.2	432.3	479.8	539.6	616.6	702.1	787.6	864.6
132.5°	353.4	365.8	378.1	408.5	443.7	485.5	538.7	604.2	678.4	755.3	825.6
135°	365.8	378.6	391.4	420.9	453.2	491.2	537.7	593.8	657.5	724.9	786.7
137.5°	377.2	389.0	400.9	429.4	460.8	495.0	535.8	584.3	637.5	694.5	749.6
140°	386.7	398.5	410.4	438.0	466.5	498.8	534.9	575.7	620.4	668.9	714.5
142.5°	396.2	407.1	418.0	444.6	472.2	501.6	533.0	568.1	604.2	644.2	682.2
145°	403.8	414.7	425.6	450.3	476.0	502.6	531.1	561.5	591.9	623.2	653.7
147.5°	413.3	422.8	432.3	455.1	478.8	502.6	528.2	554.8	581.4	607.1	632.8
150°	420.9	429.4	438.0	459.8	479.8	502.6	524.4	548.2	570.0	591.9	611.8
152.5°	428.5	436.6	444.6	462.7	481.7	499.7	519.7	540.6	559.6	577.6	594.7
155°	437.0	443.6	450.3	466.5	481.7	497.8	514.0	533.0	549.1	564.3	578.6
157.5°	444.6	449.8	455.1	468.4	482.6	495.0	509.2	524.4	537.7	551.0	562.4
160°	450.3	455.0	459.8	471.2	482.6	493.1	503.5	515.9	528.2	538.7	548.2
162.5°	455.1	458.9	462.7	472.2	481.7	489.3	497.8	507.3	516.8	525.4	533.9
165°	458.9	462.2	465.5	473.1	479.8	485.5	492.1	499.7	507.3	513.0	519.7
167.5°	462.7	465.0	467.4	473.1	478.8	481.7	486.4	492.1	498.8	503.5	507.3
170°	465.5	466.4	467.4	472.2	476.0	477.9	480.7	485.5	490.2	493.1	496.9
172.5°	467.4	467.9	468.4	472.2	475.0	475.0	476.0	478.8	482.6	484.5	487.4
175°	468.4	468.8	469.3	471.2	473.1	472.2	472.2	474.1	476.0	476.9	478.8
177.5°	469.3	469.3	469.3	470.3	472.2	470.3	469.3	470.3	471.2	472.2	473.1
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	481.3	481.8	480.5	477.8	477.4	478.3	480.9	480.0	477.8	481.8	478.3
5°	454.7	452.5	451.7	452.5	449.9	448.6	451.2	449.9	451.2	451.7	453.0
7.5°	429.0	429.4	426.8	427.3	423.8	424.6	424.6	424.6	426.0	426.8	428.6
10°	406.8	407.6	404.6	405.0	402.4	400.7	402.0	404.6	404.6	404.6	405.5
12.5°	388.9	385.0	382.8	382.4	379.3	378.4	381.0	381.9	384.1	384.1	385.4
15°	366.7	365.8	364.0	364.0	356.6	358.4	359.2	362.3	366.7	363.2	364.0
17.5°	346.6	344.4	342.2	341.4	340.5	337.9	341.4	340.9	343.6	344.0	345.3
20°	328.7	327.0	322.6	323.1	323.9	320.0	322.2	322.2	324.8	327.4	330.5
22.5°	311.3	309.5	307.4	308.2	305.6	304.8	304.8	306.9	310.0	312.2	311.7
25°	297.8	294.7	293.4	292.1	290.8	291.7	290.4	292.5	294.7	296.0	294.7
27.5°	282.5	281.2	278.6	277.3	275.1	276.0	276.8	278.6	279.9	279.9	281.2
30°	267.7	265.9	265.1	263.8	263.8	262.0	262.5	264.2	265.5	266.8	268.6
32.5°	253.3	252.0	250.7	250.7	249.8	249.4	248.9	251.6	251.6	254.2	254.2
35°	241.5	239.4	239.4	237.2	238.0	237.6	236.7	238.5	238.9	240.7	240.2
37.5°	228.5	228.5	227.6	225.4	223.7	224.1	226.3	226.3	227.6	227.1	228.5
40°	215.4	214.5	214.5	213.2	212.8	212.3	212.8	213.2	215.4	214.9	215.4
42.5°	202.3	202.7	200.6	200.6	200.6	199.2	199.7	200.1	201.0	201.9	203.2
45°	189.7	188.8	188.3	187.5	186.6	187.0	186.6	188.3	187.9	188.8	190.1
47.5°	176.1	174.8	174.4	172.6	172.6	173.5	173.1	174.4	174.8	176.1	175.3
50°	163.1	161.3	160.0	160.4	157.8	158.7	158.7	160.0	161.3	161.7	162.6
52.5°	147.8	147.4	146.9	144.7	144.3	143.9	144.3	144.7	146.5	147.8	148.2
55°	133.0	132.5	129.9	129.1	127.7	127.7	128.6	129.1	132.1	132.5	134.3
57.5°	119.5	118.2	115.1	114.7	114.7	114.7	113.4	115.1	116.0	118.2	118.2
60°	104.6	104.6	102.0	102.0	102.5	102.0	102.0	102.5	102.5	104.2	105.1
62.5°	92.9	92.4	92.4	91.6	91.1	91.6	91.1	91.1	91.6	92.9	94.2
65°	82.4	82.0	81.5	81.1	80.2	80.2	80.7	81.5	81.5	82.4	82.8
67.5°	72.4	72.4	71.5	71.5	71.1	70.6	71.1	70.6	72.4	72.4	72.8
70°	62.3	61.9	60.6	60.2	58.9	59.3	59.3	60.6	61.0	61.9	62.8
72.5°	50.1	50.1	49.3	48.4	48.8	48.0	48.0	48.4	48.4	49.7	50.1
75°	41.4	40.5	40.1	40.5	40.1	41.0	40.1	40.1	41.0	41.0	41.0
77.5°	34.0	34.0	33.6	33.6	34.0	33.6	34.0	34.0	34.0	33.6	34.0
80°	27.9	27.5	27.5	27.5	27.0	27.0	27.0	27.0	27.0	27.0	27.0
82.5°	20.9	20.9	20.5	20.9	20.9	20.5	20.9	20.5	20.5	20.9	20.9
85°	14.0	14.8	14.0	14.0	14.4	14.4	14.8	14.4	14.8	14.0	14.4
87.5°	7.4	7.8	7.8	7.4	7.4	7.8	7.8	7.8	8.3	7.4	7.8
90°	26.6	27.6	26.6	27.6	28.5	27.6	28.5	27.6	26.6	27.6	26.6
92.5°	60.4	57.0	55.1	51.3	52.3	50.4	52.3	51.3	55.1	57.0	60.4
95°	164.4	147.3	129.2	120.7	114.0	110.2	114.0	120.7	129.2	147.3	164.4
97.5°	413.2	359.1	295.5	259.4	236.6	226.1	236.6	259.4	295.5	359.1	413.2
100°	864.6	797.1	701.2	631.8	594.7	595.7	594.7	631.8	701.2	797.1	864.6
102.5°	1157.6	1121.1	1051.7	1000.4	971.0	943.4	971.0	1000.4	1051.7	1121.1	1157.6
105°	1335.8	1323.5	1279.8	1243.6	1213.2	1208.5	1213.2	1243.6	1279.8	1323.5	1335.8
107.5°	1414.2	1427.0	1421.3	1404.2	1391.9	1381.4	1391.9	1404.2	1421.3	1427.0	1414.2
110°	1416.6	1449.8	1476.4	1484.0	1482.1	1480.2	1482.1	1484.0	1476.4	1449.8	1416.6

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1362.9	1408.0	1462.2	1489.7	1499.2	1500.2	1499.2	1489.7	1462.2	1408.0	1362.9
115°	1281.2	1333.0	1404.2	1446.0	1465.0	1469.8	1465.0	1446.0	1404.2	1333.0	1281.2
117.5°	1193.8	1247.4	1321.6	1368.1	1396.6	1403.3	1396.6	1368.1	1321.6	1247.4	1193.8
120°	1111.1	1159.1	1234.1	1287.4	1310.2	1315.9	1310.2	1287.4	1234.1	1159.1	1111.1
122.5°	1046.0	1089.7	1154.3	1200.9	1226.5	1234.1	1226.5	1200.9	1154.3	1089.7	1046.0
125°	988.1	1026.1	1086.9	1128.7	1152.4	1159.1	1152.4	1128.7	1086.9	1026.1	988.1
127.5°	940.6	975.7	1030.8	1066.9	1088.8	1094.5	1088.8	1066.9	1030.8	975.7	940.6
130°	896.9	929.2	979.5	1013.7	1033.7	1041.3	1033.7	1013.7	979.5	929.2	896.9
132.5°	856.0	886.4	933.0	967.2	984.3	989.0	984.3	967.2	933.0	886.4	856.0
135°	813.8	840.8	887.4	915.9	933.0	939.6	933.0	915.9	887.4	840.8	813.8
137.5°	773.8	798.1	838.0	867.4	881.7	887.4	881.7	867.4	838.0	798.1	773.8
140°	734.9	755.3	791.4	818.0	833.2	832.3	833.2	818.0	791.4	755.3	734.9
142.5°	699.3	716.4	745.8	768.6	781.9	781.0	781.9	768.6	745.8	716.4	699.3
145°	667.4	681.2	705.0	724.9	732.5	734.4	732.5	724.9	705.0	681.2	667.4
147.5°	642.8	652.7	671.7	686.0	693.6	694.5	693.6	686.0	671.7	652.7	642.8
150°	620.8	629.9	644.2	654.6	660.3	660.3	660.3	654.6	644.2	629.9	620.8
152.5°	601.8	609.0	619.4	628.9	631.8	631.8	631.8	628.9	619.4	609.0	601.8
155°	584.3	590.0	598.5	606.1	608.0	609.0	608.0	606.1	598.5	590.0	584.3
157.5°	567.2	571.9	579.5	585.2	587.1	587.1	587.1	585.2	579.5	571.9	567.2
160°	551.5	554.8	561.5	567.2	567.2	566.2	567.2	567.2	561.5	554.8	551.5
162.5°	536.8	539.6	543.4	548.2	548.2	547.2	548.2	548.2	543.4	539.6	536.8
165°	522.0	524.4	528.2	532.0	531.1	531.1	531.1	532.0	528.2	524.4	522.0
167.5°	509.2	511.1	513.0	515.9	514.9	514.9	514.9	515.9	513.0	511.1	509.2
170°	497.8	498.8	499.7	501.6	500.7	500.7	500.7	501.6	499.7	498.8	497.8
172.5°	487.8	488.3	488.3	490.2	488.3	487.4	488.3	490.2	488.3	488.3	487.8
175°	478.8	478.8	478.8	479.8	478.8	477.9	478.8	479.8	478.8	478.8	478.8
177.5°	473.1	473.1	472.2	473.1	471.2	471.2	471.2	473.1	472.2	473.1	473.1
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	481.8	483.5	481.8	478.3	481.8	483.9	486.1	489.6	491.4	491.4	494.0
5°	454.3	457.8	456.5	455.6	459.1	461.3	464.8	469.1	473.9	477.0	480.5
7.5°	429.9	432.1	434.2	434.2	437.7	442.5	447.8	453.0	459.1	463.4	466.1
10°	408.5	410.3	411.6	413.3	418.5	423.8	430.7	437.3	442.5	447.3	451.7
12.5°	388.0	390.6	393.7	395.0	398.9	405.5	412.0	419.8	428.1	432.9	437.3
15°	368.4	369.7	373.2	377.1	380.6	387.6	395.9	404.2	411.1	418.5	422.5
17.5°	348.3	348.8	357.9	355.8	367.1	373.6	378.0	385.8	397.2	403.3	409.4
20°	328.7	333.1	337.0	339.2	345.3	352.7	365.4	371.5	380.6	386.3	391.5
22.5°	313.5	320.0	320.0	325.2	328.3	335.3	344.4	356.2	366.2	370.1	377.6
25°	300.0	303.0	308.2	310.0	315.7	321.8	327.9	340.5	351.4	356.6	361.9
27.5°	282.5	286.4	293.4	293.4	300.8	307.4	314.8	323.1	334.0	341.4	347.0
30°	269.0	272.9	276.0	280.8	283.8	289.9	303.0	309.1	318.7	325.2	332.2
32.5°	256.4	259.4	262.0	267.3	270.7	277.7	284.7	295.6	303.9	310.0	317.4
35°	242.4	245.5	248.9	252.9	258.1	264.6	271.2	280.3	288.6	294.3	300.4
37.5°	229.3	231.5	236.7	239.4	243.7	249.8	258.1	267.7	275.1	279.5	285.6
40°	216.7	218.4	222.4	227.1	230.2	235.0	243.7	252.0	261.2	266.4	271.2
42.5°	203.2	205.3	208.8	213.6	218.4	223.7	228.5	238.0	246.3	250.7	255.9
45°	191.4	192.7	195.3	200.1	204.9	208.8	216.2	225.0	232.8	236.3	242.0
47.5°	177.4	178.8	182.7	184.9	190.1	195.3	202.7	211.5	218.4	221.9	227.1
50°	163.1	164.4	167.0	171.8	175.3	180.9	187.5	194.9	203.6	208.4	211.5
52.5°	149.1	151.7	153.9	157.8	162.2	167.9	174.0	180.9	188.3	193.1	196.6
55°	135.2	137.3	139.9	142.1	147.4	152.6	159.6	166.1	172.6	177.0	180.9
57.5°	119.5	122.5	125.1	129.5	133.4	137.8	145.6	150.8	158.7	161.7	165.2
60°	105.9	109.0	111.2	114.7	118.2	123.8	129.1	135.6	142.1	146.1	150.4
62.5°	94.6	95.9	97.2	100.7	104.2	109.4	114.7	121.2	128.2	130.4	133.8
65°	83.3	84.6	86.8	89.8	92.4	95.5	101.1	106.4	112.9	116.4	117.7
67.5°	73.7	75.0	75.4	77.6	79.8	83.3	86.3	91.6	97.7	99.8	102.5
70°	62.8	65.0	65.4	67.1	68.0	70.2	73.7	77.6	82.4	86.3	88.5
72.5°	50.1	53.2	54.1	56.7	58.0	60.2	62.8	65.8	68.9	70.6	72.4
75°	41.0	41.9	42.3	44.5	46.6	49.7	51.0	52.8	55.4	57.5	59.3
77.5°	34.0	34.4	34.9	34.9	35.3	37.1	39.7	41.9	43.6	44.5	45.8
80°	27.5	27.0	27.0	27.5	27.5	27.5	28.3	31.4	32.3	34.4	34.0
82.5°	21.4	20.5	20.9	20.5	20.5	20.5	20.5	20.9	20.9	22.2	23.1
85°	14.0	14.4	14.0	14.0	13.5	14.0	13.5	13.5	13.1	13.1	12.6
87.5°	7.4	7.8	7.4	7.4	7.0	7.4	7.0	7.0	6.5	6.5	5.7
90°	25.7	24.7	23.8	22.8	23.8	20.9	18.1	15.2	12.4	11.4	10.5
92.5°	63.7	73.2	94.1	132.1	176.7	195.7	146.3	96.0	65.6	57.0	48.5
95°	181.5	231.8	342.0	457.0	563.4	501.6	345.8	204.3	123.5	105.0	86.5
97.5°	467.4	592.8	785.7	895.9	866.5	647.0	384.8	220.4	140.6	120.2	99.8
100°	932.0	1043.2	1120.1	1086.9	899.7	608.0	358.2	217.6	151.1	132.6	114.0
102.5°	1194.2	1247.4	1231.3	1096.4	838.0	551.0	335.4	221.4	163.4	146.8	130.2
105°	1348.2	1330.1	1235.1	1036.5	763.9	506.4	326.8	229.0	177.7	163.0	148.2
107.5°	1401.4	1327.3	1178.1	951.0	698.3	474.1	324.9	241.3	195.7	182.0	168.2
110°	1383.3	1263.6	1088.8	871.2	644.2	457.0	329.7	257.5	214.7	201.4	188.1

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1317.8	1180.0	1000.4	801.9	608.0	447.5	339.2	273.6	234.7	221.8	209.0
115°	1229.4	1089.7	924.4	748.7	584.3	446.5	349.6	291.7	255.6	242.8	229.9
117.5°	1140.1	1011.8	865.5	713.5	568.1	447.5	362.9	310.7	274.6	262.7	250.8
120°	1063.1	949.1	820.9	686.9	557.7	451.3	378.1	328.7	294.5	282.6	270.8
122.5°	1002.3	898.8	785.7	665.1	551.0	457.9	392.4	347.7	314.5	301.6	288.8
125°	950.1	858.9	755.3	647.0	545.3	464.6	407.6	365.8	332.5	319.7	306.9
127.5°	905.4	821.8	727.8	629.9	542.5	472.2	419.9	381.9	349.6	336.8	324.0
130°	864.6	787.6	702.1	616.6	539.6	479.8	432.3	396.2	364.8	352.0	339.2
132.5°	825.6	755.3	678.4	604.2	538.7	485.5	443.7	408.5	378.1	365.8	353.4
135°	786.7	724.9	657.5	593.8	537.7	491.2	453.2	420.9	391.4	378.6	365.8
137.5°	749.6	694.5	637.5	584.3	535.8	495.0	460.8	429.4	400.9	389.0	377.2
140°	714.5	668.9	620.4	575.7	534.9	498.8	466.5	438.0	410.4	398.5	386.7
142.5°	682.2	644.2	604.2	568.1	533.0	501.6	472.2	444.6	418.0	407.1	396.2
145°	653.7	623.2	591.9	561.5	531.1	502.6	476.0	450.3	425.6	414.7	403.8
147.5°	632.8	607.1	581.4	554.8	528.2	502.6	478.8	455.1	432.3	422.8	413.3
150°	611.8	591.9	570.0	548.2	524.4	502.6	479.8	459.8	438.0	429.4	420.9
152.5°	594.7	577.6	559.6	540.6	519.7	499.7	481.7	462.7	444.6	436.6	428.5
155°	578.6	564.3	549.1	533.0	514.0	497.8	481.7	466.5	450.3	443.6	437.0
157.5°	562.4	551.0	537.7	524.4	509.2	495.0	482.6	468.4	455.1	449.8	444.6
160°	548.2	538.7	528.2	515.9	503.5	493.1	482.6	471.2	459.8	455.0	450.3
162.5°	533.9	525.4	516.8	507.3	497.8	489.3	481.7	472.2	462.7	458.9	455.1
165°	519.7	513.0	507.3	499.7	492.1	485.5	479.8	473.1	465.5	462.2	458.9
167.5°	507.3	503.5	498.8	492.1	486.4	481.7	478.8	473.1	467.4	465.0	462.7
170°	496.9	493.1	490.2	485.5	480.7	477.9	476.0	472.2	467.4	466.4	465.5
172.5°	487.4	484.5	482.6	478.8	476.0	475.0	475.0	472.2	468.4	467.9	467.4
175°	478.8	476.9	476.0	474.1	472.2	472.2	473.1	471.2	469.3	468.8	468.4
177.5°	473.1	472.2	471.2	470.3	469.3	470.3	472.2	470.3	469.3	469.3	469.3
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	509.2	509.2	509.2	509.2
2.5°	496.1	499.2	505.3	510.5
5°	485.7	490.5	499.6	508.8
7.5°	473.0	480.5	492.2	504.9
10°	460.8	470.4	484.8	499.6
12.5°	448.6	458.7	473.9	493.1
15°	434.2	444.7	463.0	486.1
17.5°	421.6	435.5	452.1	475.2
20°	408.1	418.5	439.9	464.3
22.5°	391.1	408.5	428.6	454.3
25°	377.6	392.8	412.9	442.1
27.5°	361.0	378.9	403.3	429.0
30°	347.5	362.3	385.0	415.9
32.5°	331.8	349.2	372.8	403.3
35°	317.8	332.7	354.9	385.8
37.5°	301.3	317.4	342.2	369.7
40°	286.9	302.6	326.1	351.8
42.5°	269.4	286.0	309.5	331.3
45°	255.5	270.7	289.5	309.5
47.5°	238.5	254.6	272.9	286.9
50°	223.2	238.0	252.4	264.2
52.5°	206.7	220.2	233.2	242.0
55°	191.4	201.9	212.3	218.4
57.5°	173.5	183.5	192.3	195.8
60°	157.8	166.1	171.8	175.7
62.5°	141.3	147.4	151.7	153.9
65°	125.1	129.5	131.7	133.8
67.5°	108.6	112.5	113.8	116.4
70°	91.1	95.5	96.4	97.7
72.5°	78.0	78.0	79.8	81.5
75°	62.3	63.2	64.1	64.1
77.5°	48.8	48.8	49.7	50.1
80°	35.8	36.2	36.2	35.8
82.5°	24.4	25.3	24.4	24.0
85°	13.5	15.3	14.4	14.4
87.5°	5.7	5.7	6.5	5.7
90°	8.6	5.7	3.8	1.9
92.5°	39.0	30.4	20.9	14.3
95°	61.8	45.6	35.2	32.3
97.5°	75.1	60.8	52.3	51.3
100°	91.2	77.9	71.3	70.3
102.5°	110.2	97.9	92.2	90.3
105°	130.2	118.8	113.1	110.2
107.5°	151.1	139.7	134.0	131.1
110°	172.0	161.5	156.8	153.9

TEST NUMBER: P1012432

CATALOG NUMBER: S123RDIP-B340D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	192.9	182.4	177.7	174.8
115°	213.8	204.3	198.6	194.8
117.5°	232.8	224.2	219.5	214.7
120°	252.7	243.2	238.5	235.6
122.5°	271.7	261.3	256.5	253.7
125°	288.8	278.4	272.7	270.8
127.5°	304.0	293.6	286.9	284.1
130°	319.2	307.8	299.3	296.4
132.5°	333.5	319.2	309.7	305.9
135°	345.8	331.6	321.1	317.3
137.5°	357.2	342.0	331.6	327.8
140°	367.7	352.5	343.0	338.2
142.5°	377.2	363.9	353.4	349.6
145°	387.6	373.4	364.8	362.0
147.5°	397.1	384.8	376.2	374.3
150°	407.6	395.2	387.6	386.7
152.5°	417.1	406.6	399.0	399.0
155°	426.6	417.1	411.4	411.4
157.5°	435.1	426.6	421.8	420.9
160°	443.7	436.1	432.3	432.3
162.5°	449.4	443.7	440.8	440.8
165°	455.1	450.3	448.4	449.4
167.5°	459.8	456.0	455.1	456.0
170°	463.6	460.8	459.8	461.7
172.5°	466.5	464.6	464.6	465.5
175°	468.4	466.5	467.4	468.4
177.5°	469.3	468.4	469.3	470.3
180°	469.3	469.3	469.3	469.3

(END OF REPORT)