

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012474

Luminaire Tested: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012474
REPORT IS A COMBINATION OF REPORTS P993217 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D365UB30-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2641.0 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	91	87	91	87	84	81	74	72	70	62	60	59	50	49	49
2	90	83	77	72	83	77	72	68	65	62	59	55	52	50	45	43	42
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32
5	70	59	51	45	64	55	48	42	47	42	37	40	36	33	33	30	28
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	22
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	22	20
9	52	40	32	28	48	37	31	26	32	27	23	28	24	21	24	21	18
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5702	5702	5702	5702
5°	5707	6567	5721	4872
10°	5655	7927	5680	4255
15°	5598	8997	5598	3752
20°	5483	9704	5513	3329
25°	5399	9220	5389	3037
30°	5302	6389	5289	2753
35°	5184	4101	5159	2538
40°	5037	2896	5012	2324
45°	4782	2318	4775	2116
50°	4469	1939	4454	1872
55°	4117	1598	4084	1587
60°	3772	1321	3735	1349
65°	3365	1057	3387	1143
70°	2992	735	3072	925
75°	2537	546	2640	711
80°	2020	360	2193	533
85°	1441	171	1566	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7612 cd/sqm

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.0	2.0
10°-20°	162.8	6.2
20°-30°	256.5	9.7
30°-40°	266.7	10.1
40°-50°	228.2	8.6
50°-60°	173.9	6.6
60°-70°	111.4	4.2
70°-80°	53.4	2.0
80°-90°	15.0	0.6
90°-100°	95.3	3.6
100°-110°	279.0	10.6
110°-120°	272.5	10.3
120°-130°	217.0	8.2
130°-140°	171.2	6.5
140°-150°	127.7	4.8
150°-160°	89.0	3.4
160°-170°	52.3	2.0
170°-180°	17.0	0.6
0°-30°	471.3	17.8
0°-40°	738.0	27.9
0°-60°	1140.1	43.2
0°-90°	1320.0	50.0
90°-120°	646.8	24.5
90°-150°	1162.7	44.0
90°-180°	1321.0	50.0
0°-180°	2641.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	530	530	530	530	530	
5°	529	629	531	467	529	50
15°	506	894	506	373	506	142
25°	460	921	459	303	460	212
35°	401	400	400	247	401	251
45°	322	213	322	195	322	248
55°	227	134	225	133	227	204
65°	139	77	140	83	139	139
75°	67	33	69	43	67	72
85°	15	8	16	15	15	17
90°	1	10	1	10	1	2
95°	12	41	12	41	12	13
105°	41	452	41	452	41	44
115°	73	550	73	550	73	72
125°	101	434	101	434	101	90
135°	119	352	119	352	119	92
145°	135	275	135	275	135	85
155°	154	228	154	228	154	71
165°	168	199	168	199	168	47
175°	175	179	175	179	175	17
180°	176	176	176	176	176	

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	531.1	534.7	537.4	539.2	543.8	546.5	548.8	552.8	552.8	553.7	555.6
5°	529.3	537.0	542.4	549.7	559.2	563.7	570.1	575.5	583.2	587.3	591.4
7.5°	525.2	536.1	547.4	558.3	572.3	581.4	587.8	601.8	611.8	624.0	633.6
10°	519.7	534.7	549.2	566.0	585.0	598.6	608.2	626.8	645.8	663.0	677.6
12.5°	512.9	531.1	551.9	572.3	599.1	612.7	628.1	651.2	678.5	700.2	719.7
15°	505.7	526.5	550.1	575.1	608.6	627.7	649.9	678.0	708.4	739.7	766.4
17.5°	494.3	520.6	546.9	583.2	622.7	634.0	653.1	691.6	729.3	757.4	790.0
20°	483.0	512.5	545.6	578.2	620.9	647.2	664.9	705.7	746.0	780.0	811.3
22.5°	472.6	503.4	537.9	579.1	619.0	645.4	667.6	710.2	756.9	795.0	833.6
25°	459.9	493.4	531.5	570.5	619.0	639.0	663.5	712.9	762.4	806.4	854.0
27.5°	446.3	480.3	517.9	557.8	602.3	631.7	655.8	708.8	769.2	816.3	865.3
30°	432.7	467.6	503.9	539.7	589.6	617.7	645.4	703.9	772.8	826.8	864.4
32.5°	419.5	449.0	484.8	519.7	569.2	600.0	631.3	698.9	774.2	819.5	837.6
35°	401.4	432.2	461.2	498.4	548.3	578.7	615.4	698.4	768.3	796.4	787.3
37.5°	384.6	410.4	438.1	471.2	522.5	561.9	600.0	686.6	748.8	750.6	699.3
40°	366.0	387.3	410.4	445.4	500.7	539.7	581.0	668.5	713.4	686.6	596.4
42.5°	344.7	363.7	381.9	415.9	476.2	519.7	564.2	645.8	662.1	600.5	506.6
45°	322.0	337.4	354.2	390.0	450.3	493.4	537.9	610.9	594.1	507.0	417.7
47.5°	298.4	311.6	327.9	360.5	422.7	466.7	508.8	561.0	518.4	424.9	350.1
50°	274.8	285.3	301.1	334.7	394.6	434.5	473.5	507.5	447.6	364.6	289.3
52.5°	251.7	259.9	276.2	304.8	362.8	400.9	429.0	442.2	381.4	301.1	251.2
55°	227.2	236.3	247.2	276.2	333.8	361.9	380.5	380.0	317.5	255.3	207.7
57.5°	203.6	211.8	221.3	250.3	297.1	316.1	332.0	324.3	264.9	209.1	178.2
60°	182.8	187.3	197.7	222.2	257.6	273.9	283.0	269.8	216.3	176.4	147.4
62.5°	160.1	164.6	173.2	196.4	218.1	226.8	234.5	217.7	178.7	143.8	126.1
65°	139.2	145.1	150.6	169.2	181.0	191.4	190.5	176.4	139.7	117.0	102.5
67.5°	121.1	123.4	127.9	139.2	144.7	152.4	152.8	137.0	112.5	95.2	86.6
70°	101.6	103.9	107.0	112.5	116.1	117.9	117.0	102.9	84.8	74.4	66.7
72.5°	84.8	84.4	86.6	86.6	90.2	89.8	87.1	76.2	64.4	55.8	51.2
75°	66.7	67.1	67.6	66.7	65.3	63.5	61.2	53.1	45.4	41.3	37.2
77.5°	52.2	51.2	51.7	48.5	46.7	44.9	41.7	37.6	31.3	30.4	28.6
80°	37.2	36.7	36.3	34.9	30.8	29.0	26.8	24.5	23.1	22.2	21.8
82.5°	24.9	24.9	24.0	21.3	19.0	17.7	17.2	16.3	15.0	15.0	14.5
85°	15.0	14.5	13.6	10.9	9.5	9.5	9.5	9.5	8.6	8.6	8.2
87.5°	5.9	5.4	4.1	4.1	3.6	3.6	3.6	3.2	3.2	2.7	2.7
90°	0.7	1.4	2.1	3.2	3.9	4.2	4.6	5.7	6.8	7.8	8.9
92.5°	5.3	7.8	11.4	14.6	18.1	21.3	24.5	35.9	54.7	73.2	66.1
95°	12.1	13.2	17.1	23.1	32.4	39.3	46.2	76.4	129.4	187.7	210.8
97.5°	19.2	19.6	22.8	28.1	37.3	45.0	52.6	82.5	144.0	242.1	324.2
100°	26.3	26.7	29.2	34.1	42.7	49.6	56.5	81.4	134.0	227.5	336.7
102.5°	33.8	34.5	36.6	41.2	48.7	54.9	61.1	82.8	125.5	206.2	313.6
105°	41.2	42.3	44.4	48.7	55.5	61.0	66.5	85.7	122.3	189.5	285.8
107.5°	49.1	50.1	52.3	56.5	62.9	68.0	73.2	90.3	121.6	177.4	261.3
110°	57.6	58.7	60.4	64.3	70.4	75.4	80.3	96.3	123.4	171.0	241.0

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	65.4	66.5	68.3	72.2	78.2	83.0	87.8	102.4	126.9	167.4	227.5
115°	72.9	74.3	76.4	80.0	86.0	90.8	95.6	109.1	130.8	167.1	218.6
117.5°	80.3	82.1	83.9	87.1	93.9	98.3	102.7	116.3	135.8	167.4	212.6
120°	88.2	89.2	91.0	94.6	101.3	105.8	110.2	123.0	141.5	168.9	208.7
122.5°	94.9	96.0	97.8	101.7	108.1	112.9	117.7	130.1	146.8	171.4	206.2
125°	101.3	102.0	104.2	108.1	114.8	119.6	124.4	136.9	152.5	173.8	204.1
127.5°	106.3	107.4	109.9	113.8	121.2	126.0	130.8	142.9	157.1	176.7	203.0
130°	110.9	112.0	115.2	119.4	126.9	131.7	136.5	148.2	161.8	179.5	201.9
132.5°	114.5	115.9	119.4	124.8	132.2	136.8	141.5	152.9	166.0	181.7	201.6
135°	118.7	120.2	124.1	129.4	136.9	141.7	146.5	157.5	169.6	183.8	201.2
137.5°	122.6	124.1	128.0	133.7	141.1	145.6	150.0	160.7	172.4	185.2	200.5
140°	126.6	128.3	131.9	137.6	144.7	149.1	153.6	163.9	174.6	186.6	200.1
142.5°	130.8	132.2	136.2	141.1	148.2	152.3	156.4	166.4	176.7	187.7	199.4
145°	135.4	136.5	139.7	145.0	151.1	155.2	159.3	168.5	178.1	188.1	198.7
147.5°	140.1	140.8	144.0	148.6	154.6	158.2	161.8	170.3	179.2	188.1	197.7
150°	144.7	145.0	147.9	152.5	157.5	160.7	163.9	172.1	179.5	188.1	196.2
152.5°	149.3	149.3	152.2	156.1	160.3	163.4	166.4	173.1	180.2	187.0	194.5
155°	153.9	153.9	156.1	159.6	163.5	166.0	168.5	174.6	180.2	186.3	192.3
157.5°	157.5	157.8	159.6	162.8	166.4	168.4	170.3	175.3	180.6	185.2	190.6
160°	161.8	161.8	163.2	166.0	168.5	170.3	172.1	176.3	180.6	184.5	188.4
162.5°	165.0	165.0	166.0	168.2	170.3	171.7	173.1	176.7	180.2	183.1	186.3
165°	168.2	167.8	168.5	170.3	171.7	173.0	174.2	177.0	179.5	181.7	184.2
167.5°	170.6	170.3	170.6	172.1	173.1	174.0	174.9	177.0	179.2	180.2	182.0
170°	172.8	172.1	172.4	173.5	174.2	174.6	174.9	176.7	178.1	178.8	179.9
172.5°	174.2	173.8	173.8	174.6	174.9	175.1	175.3	176.7	177.8	177.8	178.1
175°	175.3	174.9	174.6	175.3	175.3	175.4	175.6	176.3	177.0	176.7	176.7
177.5°	176.0	175.6	175.3	175.6	175.6	175.6	175.6	176.0	176.7	176.0	175.6
180°	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	559.2	559.2	563.3	567.3	565.1	566.4	571.4	569.6	573.2	572.8	574.2
5°	601.4	606.4	610.4	619.0	620.4	619.0	627.7	629.9	634.0	629.0	631.3
7.5°	649.0	659.4	669.4	682.1	686.2	687.1	691.6	698.0	703.4	693.4	698.4
10°	695.2	711.1	731.5	742.9	752.8	756.5	760.1	764.2	770.5	776.4	771.9
12.5°	745.1	768.3	787.8	808.2	820.4	819.1	829.5	832.2	837.2	838.6	840.4
15°	785.9	818.6	830.8	861.2	863.9	873.0	884.8	895.2	896.6	893.9	893.9
17.5°	824.9	853.1	874.8	899.3	904.3	912.0	927.0	932.0	933.8	933.3	933.3
20°	856.7	875.3	912.0	932.4	940.6	950.6	961.0	967.4	968.7	970.5	967.8
22.5°	877.6	905.7	935.6	952.4	959.2	962.8	969.6	971.4	969.2	969.6	970.1
25°	893.9	921.5	939.7	944.2	943.8	939.2	934.2	925.6	924.7	921.1	913.8
27.5°	898.4	908.8	906.6	888.0	869.4	867.6	837.6	821.3	802.7	805.4	795.0
30°	873.9	860.3	828.1	781.0	761.5	729.7	696.1	661.2	647.6	632.7	660.3
32.5°	814.1	765.5	708.4	647.2	614.5	586.4	550.6	525.2	510.7	498.4	522.0
35°	723.8	648.1	572.3	514.3	487.5	462.1	428.6	415.9	397.7	399.5	401.8
37.5°	607.7	524.3	467.1	410.0	392.3	381.9	357.4	337.9	331.5	329.7	329.7
40°	498.9	430.4	379.6	334.7	321.1	312.5	293.0	283.9	277.1	275.3	277.6
42.5°	412.7	354.2	314.7	284.8	275.3	264.4	256.2	244.9	243.5	240.4	244.4
45°	346.5	295.7	266.2	244.4	236.3	232.2	223.1	216.3	213.6	213.2	216.3
47.5°	293.9	254.4	228.6	215.0	208.6	204.5	196.8	194.1	191.4	192.3	190.9
50°	246.7	217.2	200.5	188.2	184.1	180.0	175.1	172.3	171.0	171.0	170.5
52.5°	211.8	187.3	176.4	165.1	163.3	161.0	155.6	153.7	151.5	151.0	152.8
55°	181.4	164.6	153.7	146.9	145.1	140.6	138.3	136.1	134.7	133.8	134.2
57.5°	155.1	142.4	135.1	129.3	126.1	124.3	120.2	119.7	118.8	118.8	118.4
60°	133.3	124.3	115.6	112.0	109.8	107.5	107.0	104.3	102.9	103.9	103.4
62.5°	112.9	105.7	100.7	96.6	95.2	93.4	92.1	91.2	89.8	90.2	90.2
65°	94.3	88.4	84.8	81.2	80.7	78.9	78.5	77.6	77.6	77.1	78.0
67.5°	77.6	73.5	70.3	68.0	66.7	67.1	65.3	63.9	63.9	63.5	64.9
70°	61.7	59.4	56.2	53.5	51.7	51.7	49.4	49.0	49.0	49.0	48.5
72.5°	47.6	43.5	42.2	41.3	41.3	41.3	40.4	40.4	39.9	40.4	39.9
75°	35.4	34.9	34.0	33.6	33.6	33.1	32.7	32.7	32.7	32.7	32.7
77.5°	27.7	27.7	26.8	26.3	26.3	26.3	25.9	25.9	25.4	25.4	25.4
80°	20.4	20.4	19.5	19.5	19.5	19.0	19.0	19.0	19.5	19.0	19.0
82.5°	14.1	14.1	13.6	14.1	13.6	13.2	13.2	13.2	12.7	13.2	13.2
85°	8.2	8.2	7.7	7.3	7.7	7.7	7.3	7.7	7.3	7.7	7.3
87.5°	3.2	2.7	2.7	2.7	2.3	2.7	2.3	2.3	2.7	2.3	2.7
90°	8.5	8.9	9.2	9.6	10.0	10.3	10.0	10.3	10.7	10.3	10.7
92.5°	49.4	35.2	27.4	23.8	22.6	21.3	20.6	19.2	19.6	18.8	19.6
95°	171.0	128.0	86.7	67.9	61.5	55.1	48.3	45.1	42.7	41.2	42.7
97.5°	335.2	294.0	221.8	174.9	154.6	134.4	110.6	97.1	88.5	84.6	88.5
100°	406.7	419.1	390.3	348.8	323.6	298.3	262.4	236.4	222.5	222.9	222.5
102.5°	410.3	460.7	466.8	446.9	433.2	419.5	393.5	374.3	363.3	353.0	363.3
105°	387.9	462.2	497.7	504.5	499.8	495.2	478.9	465.4	454.0	452.2	454.0
107.5°	355.9	440.8	496.6	524.4	529.2	534.0	531.8	525.4	520.8	516.9	520.8
110°	326.0	407.4	472.8	517.6	530.0	542.5	552.5	555.3	554.6	553.9	554.6



TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	300.0	374.3	441.5	493.1	510.0	526.9	547.1	557.4	561.0	561.3	561.0
115°	280.1	345.9	407.8	460.0	479.4	498.8	525.4	541.1	548.2	550.0	548.2
117.5°	267.0	323.9	378.6	426.6	446.7	466.8	494.5	511.9	522.6	525.1	522.6
120°	257.0	307.2	355.1	397.8	415.8	433.7	461.8	481.7	490.2	492.4	490.2
122.5°	248.9	294.0	336.3	375.1	391.5	407.8	431.9	449.4	459.0	461.8	459.0
125°	242.1	282.6	321.4	355.5	369.7	383.9	406.7	422.3	431.2	433.7	431.2
127.5°	235.7	272.3	307.5	338.8	352.0	365.1	385.7	399.2	407.4	409.5	407.4
130°	230.7	262.7	294.7	323.5	335.6	347.7	366.5	379.3	386.8	389.6	386.8
132.5°	226.1	253.8	282.6	308.9	320.3	331.7	349.1	361.9	368.3	370.1	368.3
135°	222.2	246.0	271.3	294.4	304.5	314.6	332.0	342.7	349.1	351.6	349.1
137.5°	218.6	238.5	259.9	280.5	289.6	298.6	313.6	324.6	329.9	332.0	329.9
140°	215.4	232.1	250.3	267.3	275.0	282.6	296.1	306.1	311.8	311.4	311.8
142.5°	212.6	226.1	241.0	255.3	261.7	268.1	279.1	287.6	292.6	292.2	292.6
145°	210.1	221.5	233.2	244.6	249.8	254.9	263.8	271.3	274.1	274.8	274.1
147.5°	207.6	217.6	227.2	236.8	240.5	244.2	251.3	256.7	259.5	259.9	259.5
150°	205.1	213.3	221.5	228.9	232.3	235.7	241.0	244.9	247.1	247.1	247.1
152.5°	202.3	209.4	216.1	222.5	225.2	227.9	231.8	235.3	236.4	236.4	236.4
155°	199.4	205.5	211.2	216.5	218.6	220.8	224.0	226.8	227.5	227.9	227.5
157.5°	196.2	201.2	206.2	210.5	212.2	214.0	216.9	219.0	219.7	219.7	219.7
160°	193.0	197.7	201.6	205.1	206.4	207.6	210.1	212.2	212.2	211.9	212.2
162.5°	189.8	193.4	196.6	199.8	200.9	201.9	203.3	205.1	205.1	204.8	205.1
165°	187.0	189.8	192.0	194.5	195.4	196.2	197.7	199.1	198.7	198.7	198.7
167.5°	184.2	186.6	188.4	189.8	190.6	191.3	192.0	193.0	192.7	192.7	192.7
170°	181.7	183.4	184.5	185.9	186.2	186.6	187.0	187.7	187.4	187.4	187.4
172.5°	179.2	180.6	181.3	182.4	182.6	182.7	182.7	183.4	182.7	182.4	182.7
175°	177.4	178.1	178.5	179.2	179.2	179.2	179.2	179.5	179.2	178.8	179.2
177.5°	176.0	176.3	176.7	177.0	177.0	177.0	176.7	177.0	176.3	176.3	176.3
180°	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	571.9	569.2	567.3	566.0	564.6	568.7	563.3	557.4	553.3	550.6	549.7
5°	631.7	625.9	620.9	616.8	617.7	617.7	608.2	597.7	588.7	583.7	578.2
7.5°	701.1	694.8	684.8	682.5	680.7	669.4	659.9	640.8	629.5	618.1	608.2
10°	770.1	761.9	752.4	749.2	744.7	730.6	716.1	691.6	677.6	656.7	643.5
12.5°	834.5	824.5	815.0	812.7	805.9	793.7	768.7	743.3	719.3	697.1	673.9
15°	888.4	885.7	871.2	862.1	847.2	830.4	824.9	790.5	760.1	737.0	695.2
17.5°	933.8	921.1	907.5	901.6	895.7	876.2	856.7	821.3	788.7	754.7	727.9
20°	970.1	956.0	946.5	937.9	935.2	912.9	882.1	850.8	815.0	776.9	742.0
22.5°	971.9	970.1	963.7	958.7	953.3	938.8	914.3	875.3	837.2	795.5	749.7
25°	934.2	931.5	949.7	945.1	948.8	943.3	930.2	897.5	853.1	804.1	757.8
27.5°	820.9	848.5	877.1	887.1	893.9	913.4	919.7	901.6	865.8	813.6	761.9
30°	666.7	703.4	749.7	774.6	793.7	829.9	877.1	883.0	866.2	824.5	761.0
32.5°	523.4	556.9	594.1	623.6	649.0	723.4	786.9	832.7	840.8	819.1	763.3
35°	421.8	436.3	471.7	499.8	534.2	597.7	672.6	746.5	796.4	799.1	756.5
37.5°	347.8	355.6	386.4	402.3	422.7	478.5	548.3	644.9	722.5	759.2	737.4
40°	288.0	305.7	323.4	332.4	346.9	385.5	452.6	528.3	624.5	692.5	707.9
42.5°	249.9	257.6	268.9	281.6	290.7	324.3	369.2	438.6	525.2	620.0	662.6
45°	220.4	223.1	234.9	243.1	252.6	276.2	307.9	366.0	442.2	535.6	608.2
47.5°	195.9	201.4	207.7	212.7	219.0	237.2	264.4	306.6	373.7	457.1	535.1
50°	174.2	177.3	185.5	187.8	192.3	205.0	225.9	258.1	313.4	380.0	460.8
52.5°	153.7	159.6	162.8	166.0	170.1	180.5	194.1	220.4	262.1	324.7	393.2
55°	137.9	139.7	144.2	146.9	150.1	157.4	169.2	188.7	221.3	271.2	336.1
57.5°	122.4	122.4	127.0	129.3	132.4	137.9	148.3	163.3	186.8	224.0	283.4
60°	106.1	106.6	110.2	112.9	113.8	119.3	127.9	139.7	157.8	185.0	233.6
62.5°	91.6	93.9	95.7	96.6	99.8	102.9	110.2	118.4	131.1	155.1	189.6
65°	79.4	79.8	81.2	82.1	83.4	87.1	92.5	98.0	108.8	126.5	154.6
67.5°	65.3	67.1	68.9	68.9	70.3	72.1	77.6	82.1	90.2	100.7	119.7
70°	49.0	49.9	52.6	54.0	55.8	59.0	61.7	64.4	70.7	78.5	93.0
72.5°	40.8	40.8	41.7	42.2	42.2	44.4	48.5	51.2	54.4	59.9	69.8
75°	32.7	32.7	34.0	33.6	34.5	35.4	35.8	37.6	39.5	43.5	49.4
77.5°	25.9	26.3	26.3	26.8	26.8	27.2	27.7	28.6	29.5	31.7	34.5
80°	19.0	19.5	19.5	20.0	20.0	20.4	20.9	21.3	22.2	23.1	24.5
82.5°	13.2	13.6	13.6	14.1	13.6	14.1	14.5	14.5	15.0	15.9	16.3
85°	7.7	7.7	8.2	7.7	7.7	7.7	8.2	8.2	8.6	10.0	10.0
87.5°	2.3	2.7	2.3	2.7	2.7	2.7	2.7	3.2	3.2	3.6	4.1
90°	10.3	10.0	10.3	10.0	9.6	9.2	8.9	8.5	8.9	7.8	6.8
92.5°	19.2	20.6	21.3	22.6	23.8	27.4	35.2	49.4	66.1	73.2	54.7
95°	45.1	48.3	55.1	61.5	67.9	86.7	128.0	171.0	210.8	187.7	129.4
97.5°	97.1	110.6	134.4	154.6	174.9	221.8	294.0	335.2	324.2	242.1	144.0
100°	236.4	262.4	298.3	323.6	348.8	390.3	419.1	406.7	336.7	227.5	134.0
102.5°	374.3	393.5	419.5	433.2	446.9	466.8	460.7	410.3	313.6	206.2	125.5
105°	465.4	478.9	495.2	499.8	504.5	497.7	462.2	387.9	285.8	189.5	122.3
107.5°	525.4	531.8	534.0	529.2	524.4	496.6	440.8	355.9	261.3	177.4	121.6
110°	555.3	552.5	542.5	530.0	517.6	472.8	407.4	326.0	241.0	171.0	123.4

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	557.4	547.1	526.9	510.0	493.1	441.5	374.3	300.0	227.5	167.4	126.9
115°	541.1	525.4	498.8	479.4	460.0	407.8	345.9	280.1	218.6	167.1	130.8
117.5°	511.9	494.5	466.8	446.7	426.6	378.6	323.9	267.0	212.6	167.4	135.8
120°	481.7	461.8	433.7	415.8	397.8	355.1	307.2	257.0	208.7	168.9	141.5
122.5°	449.4	431.9	407.8	391.5	375.1	336.3	294.0	248.9	206.2	171.4	146.8
125°	422.3	406.7	383.9	369.7	355.5	321.4	282.6	242.1	204.1	173.8	152.5
127.5°	399.2	385.7	365.1	352.0	338.8	307.5	272.3	235.7	203.0	176.7	157.1
130°	379.3	366.5	347.7	335.6	323.5	294.7	262.7	230.7	201.9	179.5	161.8
132.5°	361.9	349.1	331.7	320.3	308.9	282.6	253.8	226.1	201.6	181.7	166.0
135°	342.7	332.0	314.6	304.5	294.4	271.3	246.0	222.2	201.2	183.8	169.6
137.5°	324.6	313.6	298.6	289.6	280.5	259.9	238.5	218.6	200.5	185.2	172.4
140°	306.1	296.1	282.6	275.0	267.3	250.3	232.1	215.4	200.1	186.6	174.6
142.5°	287.6	279.1	268.1	261.7	255.3	241.0	226.1	212.6	199.4	187.7	176.7
145°	271.3	263.8	254.9	249.8	244.6	233.2	221.5	210.1	198.7	188.1	178.1
147.5°	256.7	251.3	244.2	240.5	236.8	227.2	217.6	207.6	197.7	188.1	179.2
150°	244.9	241.0	235.7	232.3	228.9	221.5	213.3	205.1	196.2	188.1	179.5
152.5°	235.3	231.8	227.9	225.2	222.5	216.1	209.4	202.3	194.5	187.0	180.2
155°	226.8	224.0	220.8	218.6	216.5	211.2	205.5	199.4	192.3	186.3	180.2
157.5°	219.0	216.9	214.0	212.2	210.5	206.2	201.2	196.2	190.6	185.2	180.6
160°	212.2	210.1	207.6	206.4	205.1	201.6	197.7	193.0	188.4	184.5	180.6
162.5°	205.1	203.3	201.9	200.9	199.8	196.6	193.4	189.8	186.3	183.1	180.2
165°	199.1	197.7	196.2	195.4	194.5	192.0	189.8	187.0	184.2	181.7	179.5
167.5°	193.0	192.0	191.3	190.6	189.8	188.4	186.6	184.2	182.0	180.2	179.2
170°	187.7	187.0	186.6	186.2	185.9	184.5	183.4	181.7	179.9	178.8	178.1
172.5°	183.4	182.7	182.7	182.6	182.4	181.3	180.6	179.2	178.1	177.8	177.8
175°	179.5	179.2	179.2	179.2	179.2	178.5	178.1	177.4	176.7	176.7	177.0
177.5°	177.0	176.7	177.0	177.0	177.0	176.7	176.3	176.0	175.6	176.0	176.7
180°	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	548.3	546.0	543.8	543.8	538.8	534.2	532.0	532.9	530.2	526.5	522.9
5°	572.3	563.3	561.5	556.5	549.7	540.1	535.1	530.6	525.2	517.9	511.1
7.5°	594.6	582.8	576.4	571.4	558.3	545.1	534.2	527.0	517.5	506.6	498.4
10°	623.6	601.8	595.0	583.7	565.1	546.5	533.8	522.0	508.8	496.1	485.3
12.5°	646.7	621.8	609.1	597.7	573.7	550.1	528.8	514.3	498.4	484.4	470.3
15°	673.0	644.9	622.7	609.1	578.7	550.1	526.1	505.7	488.0	470.7	458.5
17.5°	685.7	650.3	640.4	620.9	576.9	548.3	518.8	497.1	475.7	455.8	441.3
20°	705.7	664.4	639.5	626.3	587.3	545.1	510.7	485.7	463.5	442.2	426.8
22.5°	707.0	662.1	645.8	620.9	572.8	535.6	503.4	473.0	447.2	427.2	411.3
25°	703.9	658.1	635.4	615.4	575.5	530.2	488.9	459.0	433.6	410.4	391.8
27.5°	702.5	646.3	624.9	605.0	560.1	514.3	480.3	446.3	417.2	396.8	377.8
30°	700.7	633.6	607.7	584.6	543.3	502.0	461.2	431.7	404.1	378.2	359.2
32.5°	688.9	616.3	590.0	565.5	521.1	479.8	447.6	416.3	386.4	362.4	345.1
35°	685.3	600.5	566.0	539.7	496.1	459.4	425.4	399.5	371.4	347.4	327.0
37.5°	674.8	584.1	546.9	513.4	468.0	433.1	408.2	382.3	355.1	329.3	312.9
40°	656.7	565.1	522.9	488.4	441.7	406.4	383.2	364.2	337.4	314.3	294.3
42.5°	629.9	545.6	500.2	463.9	412.2	379.1	360.1	342.0	319.3	295.2	278.9
45°	599.1	519.7	477.6	437.2	384.6	352.4	332.4	321.5	300.7	280.3	261.2
47.5°	556.9	493.0	451.2	409.5	356.0	324.7	308.8	298.0	283.4	261.2	245.8
50°	503.9	458.5	419.0	381.9	327.9	298.0	282.1	273.9	261.7	245.8	230.8
52.5°	444.9	418.6	385.9	351.5	299.3	271.2	256.7	250.3	241.3	226.3	213.6
55°	385.5	374.2	351.9	317.9	269.4	246.3	233.6	225.4	218.6	207.7	196.8
57.5°	332.4	327.0	311.6	285.3	244.4	220.4	209.5	204.1	198.6	190.5	179.6
60°	277.6	283.4	267.6	254.4	217.2	196.4	186.8	181.0	178.2	171.0	164.2
62.5°	229.9	235.4	226.3	216.3	190.0	171.4	165.5	160.1	158.3	151.9	145.1
65°	186.8	193.7	186.8	181.4	165.5	150.1	142.9	140.1	138.3	134.2	128.8
67.5°	148.8	155.6	152.4	145.6	140.6	127.9	123.8	121.1	120.2	117.0	112.5
70°	112.0	121.5	122.4	118.4	113.8	107.9	105.2	104.3	102.0	99.3	96.6
72.5°	80.7	91.6	92.1	92.1	89.3	89.3	86.6	85.3	85.3	82.5	79.4
75°	59.4	66.7	67.6	68.5	69.8	71.2	69.4	69.4	68.9	66.2	64.9
77.5°	39.5	45.8	48.1	51.2	53.1	53.1	54.0	54.9	54.0	52.6	51.7
80°	25.4	29.9	32.7	34.5	37.2	38.5	39.9	40.4	39.5	39.0	37.6
82.5°	16.8	18.1	19.5	21.8	24.9	27.2	27.2	26.8	27.7	27.2	26.8
85°	9.5	10.4	10.9	11.3	13.2	15.4	15.9	16.3	17.2	16.3	15.4
87.5°	3.6	4.1	4.1	4.1	5.0	5.4	6.8	8.6	8.2	7.3	7.3
90°	5.7	4.6	4.2	3.9	3.2	2.1	1.4	0.7	1.4	2.1	3.2
92.5°	35.9	24.5	21.3	18.1	14.6	11.4	7.8	5.3	7.8	11.4	14.6
95°	76.4	46.2	39.3	32.4	23.1	17.1	13.2	12.1	13.2	17.1	23.1
97.5°	82.5	52.6	45.0	37.3	28.1	22.8	19.6	19.2	19.6	22.8	28.1
100°	81.4	56.5	49.6	42.7	34.1	29.2	26.7	26.3	26.7	29.2	34.1
102.5°	82.8	61.1	54.9	48.7	41.2	36.6	34.5	33.8	34.5	36.6	41.2
105°	85.7	66.5	61.0	55.5	48.7	44.4	42.3	41.2	42.3	44.4	48.7
107.5°	90.3	73.2	68.0	62.9	56.5	52.3	50.1	49.1	50.1	52.3	56.5
110°	96.3	80.3	75.4	70.4	64.3	60.4	58.7	57.6	58.7	60.4	64.3

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	102.4	87.8	83.0	78.2	72.2	68.3	66.5	65.4	66.5	68.3	72.2
115°	109.1	95.6	90.8	86.0	80.0	76.4	74.3	72.9	74.3	76.4	80.0
117.5°	116.3	102.7	98.3	93.9	87.1	83.9	82.1	80.3	82.1	83.9	87.1
120°	123.0	110.2	105.8	101.3	94.6	91.0	89.2	88.2	89.2	91.0	94.6
122.5°	130.1	117.7	112.9	108.1	101.7	97.8	96.0	94.9	96.0	97.8	101.7
125°	136.9	124.4	119.6	114.8	108.1	104.2	102.0	101.3	102.0	104.2	108.1
127.5°	142.9	130.8	126.0	121.2	113.8	109.9	107.4	106.3	107.4	109.9	113.8
130°	148.2	136.5	131.7	126.9	119.4	115.2	112.0	110.9	112.0	115.2	119.4
132.5°	152.9	141.5	136.8	132.2	124.8	119.4	115.9	114.5	115.9	119.4	124.8
135°	157.5	146.5	141.7	136.9	129.4	124.1	120.2	118.7	120.2	124.1	129.4
137.5°	160.7	150.0	145.6	141.1	133.7	128.0	124.1	122.6	124.1	128.0	133.7
140°	163.9	153.6	149.1	144.7	137.6	131.9	128.3	126.6	128.3	131.9	137.6
142.5°	166.4	156.4	152.3	148.2	141.1	136.2	132.2	130.8	132.2	136.2	141.1
145°	168.5	159.3	155.2	151.1	145.0	139.7	136.5	135.4	136.5	139.7	145.0
147.5°	170.3	161.8	158.2	154.6	148.6	144.0	140.8	140.1	140.8	144.0	148.6
150°	172.1	163.9	160.7	157.5	152.5	147.9	145.0	144.7	145.0	147.9	152.5
152.5°	173.1	166.4	163.4	160.3	156.1	152.2	149.3	149.3	149.3	152.2	156.1
155°	174.6	168.5	166.0	163.5	159.6	156.1	153.9	153.9	153.9	156.1	159.6
157.5°	175.3	170.3	168.4	166.4	162.8	159.6	157.8	157.5	157.8	159.6	162.8
160°	176.3	172.1	170.3	168.5	166.0	163.2	161.8	161.8	161.8	163.2	166.0
162.5°	176.7	173.1	171.7	170.3	168.2	166.0	165.0	165.0	165.0	166.0	168.2
165°	177.0	174.2	173.0	171.7	170.3	168.5	167.8	168.2	167.8	168.5	170.3
167.5°	177.0	174.9	174.0	173.1	172.1	170.6	170.3	170.6	170.3	170.6	172.1
170°	176.7	174.9	174.6	174.2	173.5	172.4	172.1	172.8	172.1	172.4	173.5
172.5°	176.7	175.3	175.1	174.9	174.6	173.8	173.8	174.2	173.8	173.8	174.6
175°	176.3	175.6	175.4	175.3	175.3	174.6	174.9	175.3	174.9	174.6	175.3
177.5°	176.0	175.6	175.6	175.6	175.6	175.3	175.6	176.0	175.6	175.3	175.6
180°	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	522.9	520.6	519.7	517.5	512.0	508.4	504.3	501.6	502.0	499.8	501.1
5°	506.6	506.1	502.9	498.4	490.7	486.6	479.4	475.7	473.9	474.4	471.7
7.5°	493.0	488.9	486.6	479.4	472.1	463.5	457.6	454.4	451.7	449.0	447.2
10°	477.6	473.9	470.3	462.6	452.6	444.4	436.3	433.1	429.0	427.2	425.9
12.5°	461.2	459.0	454.4	445.4	434.0	426.3	416.8	415.0	409.5	405.9	405.0
15°	446.3	444.9	436.7	426.3	415.0	407.3	399.1	393.7	384.6	386.4	383.2
17.5°	430.4	424.5	419.5	405.4	400.0	388.2	378.7	376.0	369.6	365.5	361.5
20°	412.7	409.1	402.7	393.7	380.5	366.9	359.6	355.1	351.5	345.1	343.3
22.5°	395.9	391.4	385.9	374.2	362.8	351.5	341.5	337.4	332.9	328.3	325.6
25°	382.8	376.0	370.1	355.6	344.2	334.7	328.3	321.5	315.2	312.5	311.6
27.5°	362.4	358.3	352.4	338.8	328.3	317.9	312.0	307.5	300.7	297.5	294.8
30°	349.2	341.0	334.2	323.4	312.9	301.6	296.1	290.7	286.6	282.5	279.4
32.5°	331.5	325.2	319.7	308.8	298.4	288.0	282.1	273.9	271.7	268.5	264.9
35°	314.3	310.2	304.3	292.5	281.2	273.9	267.6	259.9	257.1	254.9	251.7
37.5°	298.0	292.1	288.0	276.6	266.7	258.1	253.1	246.7	244.9	242.2	239.9
40°	283.9	278.0	273.9	262.6	252.2	243.1	239.9	233.6	230.8	227.7	226.3
42.5°	268.0	263.0	257.6	249.4	238.5	229.5	223.1	219.5	215.9	214.5	211.8
45°	251.2	246.7	242.6	233.6	222.2	215.9	210.4	205.4	202.7	200.5	198.6
47.5°	236.7	232.7	227.2	217.2	208.2	202.3	196.8	191.8	189.1	186.4	184.1
50°	220.0	217.7	211.8	202.3	193.7	186.8	181.9	177.3	175.5	172.3	168.7
52.5°	205.0	200.9	195.9	188.2	180.5	172.3	165.5	162.8	159.6	157.8	154.6
55°	187.3	184.6	179.1	172.3	164.2	157.4	152.4	148.8	144.7	142.9	138.8
57.5°	172.3	167.3	164.6	156.0	148.3	141.5	137.9	134.2	129.7	127.0	125.2
60°	156.0	151.5	147.4	140.1	134.7	127.4	122.0	118.8	115.6	112.0	110.2
62.5°	140.1	136.5	131.5	125.6	118.8	112.9	108.8	104.3	102.5	98.9	97.5
65°	122.9	120.2	116.1	109.3	103.9	98.9	94.8	91.2	89.3	88.0	87.1
67.5°	107.5	103.9	101.1	95.2	89.3	85.3	83.0	80.7	78.5	77.1	75.7
70°	91.6	88.9	86.2	80.7	76.6	73.0	71.2	69.4	68.0	66.7	65.3
72.5°	75.3	73.9	71.2	67.6	64.4	61.7	60.3	58.1	56.7	54.4	53.5
75°	62.1	59.9	58.5	55.3	52.6	50.3	48.5	45.8	44.0	43.1	42.6
77.5°	49.0	48.1	46.3	43.5	42.2	39.9	37.2	36.3	35.4	35.4	34.9
80°	36.7	35.4	34.0	31.7	30.4	28.6	28.6	28.6	28.1	28.6	28.1
82.5°	24.9	24.0	23.1	21.8	21.3	21.3	21.8	21.8	21.8	21.8	21.8
85°	14.5	14.5	14.5	15.0	14.5	14.5	15.0	15.4	15.0	15.0	14.5
87.5°	6.8	6.8	7.3	7.3	7.7	7.7	7.7	7.7	7.7	7.7	8.2
90°	3.9	4.2	4.6	5.7	6.8	7.8	8.9	8.5	8.9	9.2	9.6
92.5°	18.1	21.3	24.5	35.9	54.7	73.2	66.1	49.4	35.2	27.4	23.8
95°	32.4	39.3	46.2	76.4	129.4	187.7	210.8	171.0	128.0	86.7	67.9
97.5°	37.3	45.0	52.6	82.5	144.0	242.1	324.2	335.2	294.0	221.8	174.9
100°	42.7	49.6	56.5	81.4	134.0	227.5	336.7	406.7	419.1	390.3	348.8
102.5°	48.7	54.9	61.1	82.8	125.5	206.2	313.6	410.3	460.7	466.8	446.9
105°	55.5	61.0	66.5	85.7	122.3	189.5	285.8	387.9	462.2	497.7	504.5
107.5°	62.9	68.0	73.2	90.3	121.6	177.4	261.3	355.9	440.8	496.6	524.4
110°	70.4	75.4	80.3	96.3	123.4	171.0	241.0	326.0	407.4	472.8	517.6

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	78.2	83.0	87.8	102.4	126.9	167.4	227.5	300.0	374.3	441.5	493.1
115°	86.0	90.8	95.6	109.1	130.8	167.1	218.6	280.1	345.9	407.8	460.0
117.5°	93.9	98.3	102.7	116.3	135.8	167.4	212.6	267.0	323.9	378.6	426.6
120°	101.3	105.8	110.2	123.0	141.5	168.9	208.7	257.0	307.2	355.1	397.8
122.5°	108.1	112.9	117.7	130.1	146.8	171.4	206.2	248.9	294.0	336.3	375.1
125°	114.8	119.6	124.4	136.9	152.5	173.8	204.1	242.1	282.6	321.4	355.5
127.5°	121.2	126.0	130.8	142.9	157.1	176.7	203.0	235.7	272.3	307.5	338.8
130°	126.9	131.7	136.5	148.2	161.8	179.5	201.9	230.7	262.7	294.7	323.5
132.5°	132.2	136.8	141.5	152.9	166.0	181.7	201.6	226.1	253.8	282.6	308.9
135°	136.9	141.7	146.5	157.5	169.6	183.8	201.2	222.2	246.0	271.3	294.4
137.5°	141.1	145.6	150.0	160.7	172.4	185.2	200.5	218.6	238.5	259.9	280.5
140°	144.7	149.1	153.6	163.9	174.6	186.6	200.1	215.4	232.1	250.3	267.3
142.5°	148.2	152.3	156.4	166.4	176.7	187.7	199.4	212.6	226.1	241.0	255.3
145°	151.1	155.2	159.3	168.5	178.1	188.1	198.7	210.1	221.5	233.2	244.6
147.5°	154.6	158.2	161.8	170.3	179.2	188.1	197.7	207.6	217.6	227.2	236.8
150°	157.5	160.7	163.9	172.1	179.5	188.1	196.2	205.1	213.3	221.5	228.9
152.5°	160.3	163.4	166.4	173.1	180.2	187.0	194.5	202.3	209.4	216.1	222.5
155°	163.5	166.0	168.5	174.6	180.2	186.3	192.3	199.4	205.5	211.2	216.5
157.5°	166.4	168.4	170.3	175.3	180.6	185.2	190.6	196.2	201.2	206.2	210.5
160°	168.5	170.3	172.1	176.3	180.6	184.5	188.4	193.0	197.7	201.6	205.1
162.5°	170.3	171.7	173.1	176.7	180.2	183.1	186.3	189.8	193.4	196.6	199.8
165°	171.7	173.0	174.2	177.0	179.5	181.7	184.2	187.0	189.8	192.0	194.5
167.5°	173.1	174.0	174.9	177.0	179.2	180.2	182.0	184.2	186.6	188.4	189.8
170°	174.2	174.6	174.9	176.7	178.1	178.8	179.9	181.7	183.4	184.5	185.9
172.5°	174.9	175.1	175.3	176.7	177.8	177.8	178.1	179.2	180.6	181.3	182.4
175°	175.3	175.4	175.6	176.3	177.0	176.7	176.7	177.4	178.1	178.5	179.2
177.5°	175.6	175.6	175.6	176.0	176.7	176.0	175.6	176.0	176.3	176.7	177.0
180°	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	500.7	501.1	499.8	497.1	496.6	497.5	500.2	499.3	497.1	501.1	497.5
5°	473.0	470.7	469.8	470.7	468.0	466.7	469.4	468.0	469.4	469.8	471.2
7.5°	446.3	446.7	444.0	444.4	440.8	441.7	441.7	441.7	443.1	444.0	445.8
10°	423.1	424.0	420.9	421.3	418.6	416.8	418.1	420.9	420.9	420.9	421.8
12.5°	404.5	400.5	398.2	397.7	394.6	393.7	396.4	397.3	399.5	399.5	400.9
15°	381.4	380.5	378.7	378.7	371.0	372.8	373.7	376.9	381.4	377.8	378.7
17.5°	360.5	358.3	356.0	355.1	354.2	351.5	355.1	354.6	357.4	357.8	359.2
20°	342.0	340.1	335.6	336.1	337.0	332.9	335.1	335.1	337.9	340.6	343.8
22.5°	323.8	322.0	319.7	320.6	317.9	317.0	317.0	319.3	322.5	324.7	324.3
25°	309.8	306.6	305.2	303.9	302.5	303.4	302.0	304.3	306.6	307.9	306.6
27.5°	293.9	292.5	289.8	288.4	286.2	287.1	288.0	289.8	291.2	291.2	292.5
30°	278.5	276.6	275.7	274.4	274.4	272.6	273.0	274.8	276.2	277.6	279.4
32.5°	263.5	262.1	260.8	260.8	259.9	259.4	259.0	261.7	261.7	264.4	264.4
35°	251.2	249.0	249.0	246.7	247.6	247.2	246.3	248.1	248.5	250.3	249.9
37.5°	237.6	237.6	236.7	234.5	232.7	233.1	235.4	235.4	236.7	236.3	237.6
40°	224.0	223.1	223.1	221.8	221.3	220.9	221.3	221.8	224.0	223.6	224.0
42.5°	210.4	210.9	208.6	208.6	208.6	207.3	207.7	208.2	209.1	210.0	211.3
45°	197.3	196.4	195.9	195.0	194.1	194.6	194.1	195.9	195.5	196.4	197.7
47.5°	183.2	181.9	181.4	179.6	179.6	180.5	180.0	181.4	181.9	183.2	182.3
50°	169.6	167.8	166.4	166.9	164.2	165.1	165.1	166.4	167.8	168.3	169.2
52.5°	153.7	153.3	152.8	150.6	150.1	149.7	150.1	150.6	152.4	153.7	154.2
55°	138.3	137.9	135.1	134.2	132.9	132.9	133.8	134.2	137.4	137.9	139.7
57.5°	124.3	122.9	119.7	119.3	119.3	119.3	117.9	119.7	120.6	122.9	122.9
60°	108.8	108.8	106.1	106.1	106.6	106.1	106.1	106.6	106.6	108.4	109.3
62.5°	96.6	96.1	96.1	95.2	94.8	95.2	94.8	94.8	95.2	96.6	98.0
65°	85.7	85.3	84.8	84.4	83.4	83.4	83.9	84.8	84.8	85.7	86.2
67.5°	75.3	75.3	74.4	74.4	73.9	73.5	73.9	73.5	75.3	75.3	75.7
70°	64.9	64.4	63.0	62.6	61.2	61.7	61.7	63.0	63.5	64.4	65.3
72.5°	52.2	52.2	51.2	50.3	50.8	49.9	49.9	50.3	50.3	51.7	52.2
75°	43.1	42.2	41.7	42.2	41.7	42.6	41.7	41.7	42.6	42.6	42.6
77.5°	35.4	35.4	34.9	34.9	35.4	34.9	35.4	35.4	35.4	34.9	35.4
80°	29.0	28.6	28.6	28.6	28.1	28.1	28.1	28.1	28.1	28.1	28.1
82.5°	21.8	21.8	21.3	21.8	21.8	21.3	21.8	21.3	21.3	21.8	21.8
85°	14.5	15.4	14.5	14.5	15.0	15.0	15.4	15.0	15.4	14.5	15.0
87.5°	7.7	8.2	8.2	7.7	7.7	8.2	8.2	8.2	8.6	7.7	8.2
90°	10.0	10.3	10.0	10.3	10.7	10.3	10.7	10.3	10.0	10.3	10.0
92.5°	22.6	21.3	20.6	19.2	19.6	18.8	19.6	19.2	20.6	21.3	22.6
95°	61.5	55.1	48.3	45.1	42.7	41.2	42.7	45.1	48.3	55.1	61.5
97.5°	154.6	134.4	110.6	97.1	88.5	84.6	88.5	97.1	110.6	134.4	154.6
100°	323.6	298.3	262.4	236.4	222.5	222.9	222.5	236.4	262.4	298.3	323.6
102.5°	433.2	419.5	393.5	374.3	363.3	353.0	363.3	374.3	393.5	419.5	433.2
105°	499.8	495.2	478.9	465.4	454.0	452.2	454.0	465.4	478.9	495.2	499.8
107.5°	529.2	534.0	531.8	525.4	520.8	516.9	520.8	525.4	531.8	534.0	529.2
110°	530.0	542.5	552.5	555.3	554.6	553.9	554.6	555.3	552.5	542.5	530.0

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	510.0	526.9	547.1	557.4	561.0	561.3	561.0	557.4	547.1	526.9	510.0
115°	479.4	498.8	525.4	541.1	548.2	550.0	548.2	541.1	525.4	498.8	479.4
117.5°	446.7	466.8	494.5	511.9	522.6	525.1	522.6	511.9	494.5	466.8	446.7
120°	415.8	433.7	461.8	481.7	490.2	492.4	490.2	481.7	461.8	433.7	415.8
122.5°	391.5	407.8	431.9	449.4	459.0	461.8	459.0	449.4	431.9	407.8	391.5
125°	369.7	383.9	406.7	422.3	431.2	433.7	431.2	422.3	406.7	383.9	369.7
127.5°	352.0	365.1	385.7	399.2	407.4	409.5	407.4	399.2	385.7	365.1	352.0
130°	335.6	347.7	366.5	379.3	386.8	389.6	386.8	379.3	366.5	347.7	335.6
132.5°	320.3	331.7	349.1	361.9	368.3	370.1	368.3	361.9	349.1	331.7	320.3
135°	304.5	314.6	332.0	342.7	349.1	351.6	349.1	342.7	332.0	314.6	304.5
137.5°	289.6	298.6	313.6	324.6	329.9	332.0	329.9	324.6	313.6	298.6	289.6
140°	275.0	282.6	296.1	306.1	311.8	311.4	311.8	306.1	296.1	282.6	275.0
142.5°	261.7	268.1	279.1	287.6	292.6	292.2	292.6	287.6	279.1	268.1	261.7
145°	249.8	254.9	263.8	271.3	274.1	274.8	274.1	271.3	263.8	254.9	249.8
147.5°	240.5	244.2	251.3	256.7	259.5	259.9	259.5	256.7	251.3	244.2	240.5
150°	232.3	235.7	241.0	244.9	247.1	247.1	247.1	244.9	241.0	235.7	232.3
152.5°	225.2	227.9	231.8	235.3	236.4	236.4	236.4	235.3	231.8	227.9	225.2
155°	218.6	220.8	224.0	226.8	227.5	227.9	227.5	226.8	224.0	220.8	218.6
157.5°	212.2	214.0	216.9	219.0	219.7	219.7	219.7	219.0	216.9	214.0	212.2
160°	206.4	207.6	210.1	212.2	212.2	211.9	212.2	212.2	210.1	207.6	206.4
162.5°	200.9	201.9	203.3	205.1	205.1	204.8	205.1	205.1	203.3	201.9	200.9
165°	195.4	196.2	197.7	199.1	198.7	198.7	198.7	199.1	197.7	196.2	195.4
167.5°	190.6	191.3	192.0	193.0	192.7	192.7	192.7	193.0	192.0	191.3	190.6
170°	186.2	186.6	187.0	187.7	187.4	187.4	187.4	187.7	187.0	186.6	186.2
172.5°	182.6	182.7	182.7	183.4	182.7	182.4	182.7	183.4	182.7	182.7	182.6
175°	179.2	179.2	179.2	179.5	179.2	178.8	179.2	179.5	179.2	179.2	179.2
177.5°	177.0	177.0	176.7	177.0	176.3	176.3	176.3	177.0	176.7	177.0	177.0
180°	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	501.1	502.9	501.1	497.5	501.1	503.4	505.7	509.3	511.1	511.1	513.8
5°	472.6	476.2	474.8	473.9	477.6	479.8	483.4	488.0	493.0	496.1	499.8
7.5°	447.2	449.4	451.7	451.7	455.3	460.3	465.8	471.2	477.6	482.1	484.8
10°	424.9	426.8	428.1	429.9	435.4	440.8	448.1	454.9	460.3	465.3	469.8
12.5°	403.6	406.4	409.5	410.9	415.0	421.8	428.6	436.7	445.4	450.3	454.9
15°	383.2	384.6	388.2	392.3	395.9	403.2	411.8	420.4	427.7	435.4	439.5
17.5°	362.4	362.8	372.3	370.1	381.9	388.7	393.2	401.4	413.2	419.5	425.9
20°	342.0	346.5	350.6	352.8	359.2	366.9	380.0	386.4	395.9	401.8	407.3
22.5°	326.1	332.9	332.9	338.3	341.5	348.8	358.3	370.5	381.0	385.0	392.7
25°	312.0	315.2	320.6	322.5	328.3	334.7	341.0	354.2	365.5	371.0	376.4
27.5°	293.9	298.0	305.2	305.2	312.9	319.7	327.4	336.1	347.4	355.1	361.0
30°	279.8	283.9	287.1	292.1	295.2	301.6	315.2	321.5	331.5	338.3	345.6
32.5°	266.7	269.8	272.6	278.0	281.6	288.9	296.1	307.5	316.1	322.5	330.2
35°	252.2	255.3	259.0	263.0	268.5	275.3	282.1	291.6	300.2	306.1	312.5
37.5°	238.5	240.8	246.3	249.0	253.5	259.9	268.5	278.5	286.2	290.7	297.1
40°	225.4	227.2	231.3	236.3	239.5	244.4	253.5	262.1	271.7	277.1	282.1
42.5°	211.3	213.6	217.2	222.2	227.2	232.7	237.6	247.6	256.2	260.8	266.2
45°	199.1	200.5	203.2	208.2	213.2	217.2	224.9	234.0	242.2	245.8	251.7
47.5°	184.6	185.9	190.0	192.3	197.7	203.2	210.9	220.0	227.2	230.8	236.3
50°	169.6	171.0	173.7	178.7	182.3	188.2	195.0	202.7	211.8	216.8	220.0
52.5°	155.1	157.8	160.1	164.2	168.7	174.6	181.0	188.2	195.9	200.9	204.5
55°	140.6	142.9	145.6	147.8	153.3	158.7	166.0	172.8	179.6	184.1	188.2
57.5°	124.3	127.4	130.2	134.7	138.8	143.3	151.5	156.9	165.1	168.3	171.9
60°	110.2	113.4	115.6	119.3	122.9	128.8	134.2	141.0	147.8	151.9	156.5
62.5°	98.4	99.8	101.1	104.8	108.4	113.8	119.3	126.1	133.3	135.6	139.2
65°	86.6	88.0	90.2	93.4	96.1	99.3	105.2	110.7	117.5	121.1	122.4
67.5°	76.6	78.0	78.5	80.7	83.0	86.6	89.8	95.2	101.6	103.9	106.6
70°	65.3	67.6	68.0	69.8	70.7	73.0	76.6	80.7	85.7	89.8	92.1
72.5°	52.2	55.3	56.2	59.0	60.3	62.6	65.3	68.5	71.7	73.5	75.3
75°	42.6	43.5	44.0	46.3	48.5	51.7	53.1	54.9	57.6	59.9	61.7
77.5°	35.4	35.8	36.3	36.3	36.7	38.5	41.3	43.5	45.4	46.3	47.6
80°	28.6	28.1	28.1	28.6	28.6	28.6	29.5	32.7	33.6	35.8	35.4
82.5°	22.2	21.3	21.8	21.3	21.3	21.3	21.3	21.8	21.8	23.1	24.0
85°	14.5	15.0	14.5	14.5	14.1	14.5	14.1	14.1	13.6	13.6	13.2
87.5°	7.7	8.2	7.7	7.7	7.3	7.7	7.3	7.3	6.8	6.8	5.9
90°	9.6	9.2	8.9	8.5	8.9	7.8	6.8	5.7	4.6	4.2	3.9
92.5°	23.8	27.4	35.2	49.4	66.1	73.2	54.7	35.9	24.5	21.3	18.1
95°	67.9	86.7	128.0	171.0	210.8	187.7	129.4	76.4	46.2	39.3	32.4
97.5°	174.9	221.8	294.0	335.2	324.2	242.1	144.0	82.5	52.6	45.0	37.3
100°	348.8	390.3	419.1	406.7	336.7	227.5	134.0	81.4	56.5	49.6	42.7
102.5°	446.9	466.8	460.7	410.3	313.6	206.2	125.5	82.8	61.1	54.9	48.7
105°	504.5	497.7	462.2	387.9	285.8	189.5	122.3	85.7	66.5	61.0	55.5
107.5°	524.4	496.6	440.8	355.9	261.3	177.4	121.6	90.3	73.2	68.0	62.9
110°	517.6	472.8	407.4	326.0	241.0	171.0	123.4	96.3	80.3	75.4	70.4

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	493.1	441.5	374.3	300.0	227.5	167.4	126.9	102.4	87.8	83.0	78.2
115°	460.0	407.8	345.9	280.1	218.6	167.1	130.8	109.1	95.6	90.8	86.0
117.5°	426.6	378.6	323.9	267.0	212.6	167.4	135.8	116.3	102.7	98.3	93.9
120°	397.8	355.1	307.2	257.0	208.7	168.9	141.5	123.0	110.2	105.8	101.3
122.5°	375.1	336.3	294.0	248.9	206.2	171.4	146.8	130.1	117.7	112.9	108.1
125°	355.5	321.4	282.6	242.1	204.1	173.8	152.5	136.9	124.4	119.6	114.8
127.5°	338.8	307.5	272.3	235.7	203.0	176.7	157.1	142.9	130.8	126.0	121.2
130°	323.5	294.7	262.7	230.7	201.9	179.5	161.8	148.2	136.5	131.7	126.9
132.5°	308.9	282.6	253.8	226.1	201.6	181.7	166.0	152.9	141.5	136.8	132.2
135°	294.4	271.3	246.0	222.2	201.2	183.8	169.6	157.5	146.5	141.7	136.9
137.5°	280.5	259.9	238.5	218.6	200.5	185.2	172.4	160.7	150.0	145.6	141.1
140°	267.3	250.3	232.1	215.4	200.1	186.6	174.6	163.9	153.6	149.1	144.7
142.5°	255.3	241.0	226.1	212.6	199.4	187.7	176.7	166.4	156.4	152.3	148.2
145°	244.6	233.2	221.5	210.1	198.7	188.1	178.1	168.5	159.3	155.2	151.1
147.5°	236.8	227.2	217.6	207.6	197.7	188.1	179.2	170.3	161.8	158.2	154.6
150°	228.9	221.5	213.3	205.1	196.2	188.1	179.5	172.1	163.9	160.7	157.5
152.5°	222.5	216.1	209.4	202.3	194.5	187.0	180.2	173.1	166.4	163.4	160.3
155°	216.5	211.2	205.5	199.4	192.3	186.3	180.2	174.6	168.5	166.0	163.5
157.5°	210.5	206.2	201.2	196.2	190.6	185.2	180.6	175.3	170.3	168.4	166.4
160°	205.1	201.6	197.7	193.0	188.4	184.5	180.6	176.3	172.1	170.3	168.5
162.5°	199.8	196.6	193.4	189.8	186.3	183.1	180.2	176.7	173.1	171.7	170.3
165°	194.5	192.0	189.8	187.0	184.2	181.7	179.5	177.0	174.2	173.0	171.7
167.5°	189.8	188.4	186.6	184.2	182.0	180.2	179.2	177.0	174.9	174.0	173.1
170°	185.9	184.5	183.4	181.7	179.9	178.8	178.1	176.7	174.9	174.6	174.2
172.5°	182.4	181.3	180.6	179.2	178.1	177.8	177.8	176.7	175.3	175.1	174.9
175°	179.2	178.5	178.1	177.4	176.7	176.7	177.0	176.3	175.6	175.4	175.3
177.5°	177.0	176.7	176.3	176.0	175.6	176.0	176.7	176.0	175.6	175.6	175.6
180°	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6	175.6

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	529.7	529.7	529.7	529.7
2.5°	516.1	519.3	525.6	531.1
5°	505.2	510.2	519.7	529.3
7.5°	492.1	499.8	512.0	525.2
10°	479.4	489.3	504.3	519.7
12.5°	466.7	477.1	493.0	512.9
15°	451.7	462.6	481.6	505.7
17.5°	438.6	453.1	470.3	494.3
20°	424.5	435.4	457.6	483.0
22.5°	406.8	424.9	445.8	472.6
25°	392.7	408.6	429.5	459.9
27.5°	375.5	394.1	419.5	446.3
30°	361.5	376.9	400.5	432.7
32.5°	345.1	363.3	387.8	419.5
35°	330.6	346.0	369.2	401.4
37.5°	313.4	330.2	356.0	384.6
40°	298.4	314.7	339.2	366.0
42.5°	280.3	297.5	322.0	344.7
45°	265.8	281.6	301.1	322.0
47.5°	248.1	264.9	283.9	298.4
50°	232.2	247.6	262.6	274.8
52.5°	215.0	229.0	242.6	251.7
55°	199.1	210.0	220.9	227.2
57.5°	180.5	190.9	200.0	203.6
60°	164.2	172.8	178.7	182.8
62.5°	146.9	153.3	157.8	160.1
65°	130.2	134.7	137.0	139.2
67.5°	112.9	117.0	118.4	121.1
70°	94.8	99.3	100.2	101.6
72.5°	81.2	81.2	83.0	84.8
75°	64.9	65.8	66.7	66.7
77.5°	50.8	50.8	51.7	52.2
80°	37.2	37.6	37.6	37.2
82.5°	25.4	26.3	25.4	24.9
85°	14.1	15.9	15.0	15.0
87.5°	5.9	5.9	6.8	5.9
90°	3.2	2.1	1.4	0.7
92.5°	14.6	11.4	7.8	5.3
95°	23.1	17.1	13.2	12.1
97.5°	28.1	22.8	19.6	19.2
100°	34.1	29.2	26.7	26.3
102.5°	41.2	36.6	34.5	33.8
105°	48.7	44.4	42.3	41.2
107.5°	56.5	52.3	50.1	49.1
110°	64.3	60.4	58.7	57.6

TEST NUMBER: P1012474

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	72.2	68.3	66.5	65.4
115°	80.0	76.4	74.3	72.9
117.5°	87.1	83.9	82.1	80.3
120°	94.6	91.0	89.2	88.2
122.5°	101.7	97.8	96.0	94.9
125°	108.1	104.2	102.0	101.3
127.5°	113.8	109.9	107.4	106.3
130°	119.4	115.2	112.0	110.9
132.5°	124.8	119.4	115.9	114.5
135°	129.4	124.1	120.2	118.7
137.5°	133.7	128.0	124.1	122.6
140°	137.6	131.9	128.3	126.6
142.5°	141.1	136.2	132.2	130.8
145°	145.0	139.7	136.5	135.4
147.5°	148.6	144.0	140.8	140.1
150°	152.5	147.9	145.0	144.7
152.5°	156.1	152.2	149.3	149.3
155°	159.6	156.1	153.9	153.9
157.5°	162.8	159.6	157.8	157.5
160°	166.0	163.2	161.8	161.8
162.5°	168.2	166.0	165.0	165.0
165°	170.3	168.5	167.8	168.2
167.5°	172.1	170.6	170.3	170.6
170°	173.5	172.4	172.1	172.8
172.5°	174.6	173.8	173.8	174.2
175°	175.3	174.6	174.9	175.3
177.5°	175.6	175.3	175.6	176.0
180°	175.6	175.6	175.6	175.6

(END OF REPORT)