

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012519

Luminaire Tested: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012519
REPORT IS A COMBINATION OF REPORTS P993274 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D585UB50-4F0-XX-W2A-A1
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3208.0 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	47	47	40
1	96	92	88	85	87	84	81	78	69	66	65	55	53	52	42	41	40	40	40	34
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	37	36	35	35	35	29
3	80	71	64	59	73	65	59	54	54	50	46	43	40	38	34	32	30	30	30	25
4	74	63	56	50	67	58	52	47	48	43	40	39	35	33	30	28	26	26	26	22
5	68	57	49	43	61	52	45	40	43	38	34	35	31	29	27	25	23	23	23	20
6	62	51	43	38	57	47	40	35	39	34	30	32	28	25	25	22	20	20	20	17
7	58	46	38	33	53	42	36	31	35	30	27	29	25	22	23	20	18	18	18	16
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	18	16	16	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	20	17	15	15	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	18	16	14	14	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5481	5481	5481	5481
5°	5486	6313	5500	4683
10°	5437	7621	5461	4091
15°	5381	8649	5381	3607
20°	5270	9329	5300	3200
25°	5190	8864	5180	2920
30°	5096	6141	5086	2645
35°	4982	3943	4960	2439
40°	4842	2784	4818	2233
45°	4596	2228	4591	2033
50°	4296	1864	4282	1800
55°	3957	1536	3926	1525
60°	3625	1269	3590	1297
65°	3234	1016	3256	1100
70°	2877	706	2954	889
75°	2438	524	2537	684
80°	1944	347	2106	512
85°	1383	164	1508	319

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7318 cd/sqm

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.6
10°-20°	156.5	4.9
20°-30°	246.6	7.7
30°-40°	256.4	8.0
40°-50°	219.3	6.8
50°-60°	167.2	5.2
60°-70°	107.1	3.3
70°-80°	51.3	1.6
80°-90°	15.0	0.5
90°-100°	45.0	1.4
100°-110°	136.3	4.2
110°-120°	232.1	7.2
120°-130°	305.3	9.5
130°-140°	343.2	10.7
140°-150°	337.4	10.5
150°-160°	284.0	8.9
160°-170°	189.1	5.9
170°-180°	66.2	2.1
0°-30°	453.1	14.1
0°-40°	709.5	22.1
0°-60°	1096.0	34.2
0°-90°	1269.5	39.6
90°-120°	413.4	12.9
90°-150°	1399.2	43.6
90°-180°	1939.0	60.4
0°-180°	3208.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	509	605	510	449	509	48
15°	486	859	486	358	486	137
25°	442	886	441	292	442	204
35°	386	384	384	238	386	241
45°	310	205	309	187	310	238
55°	218	129	217	128	218	196
65°	134	74	135	80	134	134
75°	64	31	67	41	64	69
85°	14	7	16	14	14	16
90°	0	16	0	16	0	3
95°	32	43	32	43	32	36
105°	124	131	124	131	124	132
115°	234	234	234	234	234	231
125°	342	338	342	338	342	305
135°	444	443	444	443	444	342
145°	538	538	538	538	538	336
155°	616	615	616	615	616	284
165°	671	669	671	669	671	189
175°	698	695	698	695	698	66
180°	700	700	700	700	700	

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	510.5	514.0	516.6	518.4	522.7	525.4	527.5	531.5	531.5	532.3	534.1
5°	508.8	516.2	521.4	528.4	537.6	541.9	548.0	553.3	560.7	564.6	568.5
7.5°	504.9	515.3	526.2	536.7	550.2	558.9	565.0	578.5	588.1	599.9	609.1
10°	499.6	514.0	528.0	544.1	562.4	575.5	584.7	602.5	620.8	637.4	651.4
12.5°	493.1	510.5	530.6	550.2	575.9	589.0	603.8	626.1	652.2	673.2	691.9
15°	486.1	506.2	528.8	552.8	585.1	603.4	624.8	651.8	681.0	711.1	736.8
17.5°	475.2	500.5	525.8	560.7	598.6	609.5	627.8	664.9	701.1	728.1	759.5
20°	464.3	492.7	524.5	555.9	596.9	622.1	639.1	678.4	717.2	749.9	780.0
22.5°	454.3	483.9	517.1	556.7	595.1	620.4	641.8	682.7	727.7	764.3	801.3
25°	442.1	474.3	511.0	548.5	595.1	614.3	637.8	685.4	732.9	775.2	821.0
27.5°	429.0	461.7	497.9	536.3	579.0	607.3	630.4	681.4	739.4	784.8	831.9
30°	415.9	449.5	484.4	518.8	566.8	593.8	620.4	676.6	742.9	794.8	831.0
32.5°	403.3	431.6	466.1	499.6	547.2	576.8	606.9	671.8	744.2	787.8	805.3
35°	385.8	415.5	443.4	479.1	527.1	556.3	591.6	671.4	738.6	765.6	756.9
37.5°	369.7	394.6	421.2	453.0	502.2	540.2	576.8	660.1	719.8	721.5	672.3
40°	351.8	372.3	394.6	428.1	481.3	518.8	558.5	642.6	685.8	660.1	573.3
42.5°	331.3	349.7	367.1	399.8	457.8	499.6	542.4	620.8	636.5	577.2	487.0
45°	309.5	324.4	340.5	374.9	432.9	474.3	517.1	587.3	571.1	487.4	401.5
47.5°	286.9	299.5	315.2	346.6	406.3	448.6	489.2	539.3	498.3	408.5	336.6
50°	264.2	274.2	289.5	321.8	379.3	417.7	455.2	487.9	430.3	350.5	278.2
52.5°	242.0	249.8	265.5	293.0	348.8	385.4	412.4	425.1	366.7	289.5	241.5
55°	218.4	227.1	237.6	265.5	320.9	347.9	365.8	365.4	305.2	245.5	199.7
57.5°	195.8	203.6	212.8	240.7	285.6	303.9	319.1	311.7	254.6	201.0	171.3
60°	175.7	180.1	190.1	213.6	247.6	263.3	272.1	259.4	208.0	169.6	141.7
62.5°	153.9	158.3	166.5	188.8	209.7	218.0	225.4	209.3	171.8	138.2	121.2
65°	133.8	139.5	144.7	162.6	174.0	184.0	183.1	169.6	134.3	112.5	98.5
67.5°	116.4	118.6	122.9	133.8	139.1	146.5	146.9	131.7	108.1	91.6	83.3
70°	97.7	99.8	102.9	108.1	111.6	113.4	112.5	99.0	81.5	71.5	64.1
72.5°	81.5	81.1	83.3	83.3	86.8	86.3	83.7	73.2	61.9	53.6	49.3
75°	64.1	64.5	65.0	64.1	62.8	61.0	58.9	51.0	43.6	39.7	35.8
77.5°	50.1	49.3	49.7	46.6	44.9	43.2	40.1	36.2	30.1	29.2	27.5
80°	35.8	35.3	34.9	33.6	29.6	27.9	25.7	23.5	22.2	21.4	20.9
82.5°	24.0	24.0	23.1	20.5	18.3	17.0	16.6	15.7	14.4	14.4	14.0
85°	14.4	14.0	13.1	10.5	9.2	9.2	9.2	9.2	8.3	8.3	7.8
87.5°	5.7	5.2	3.9	3.9	3.5	3.5	3.5	3.1	3.1	2.6	2.6
90°	0.5	1.7	2.9	4.2	5.4	6.0	6.8	8.4	10.0	11.6	13.2
92.5°	16.5	17.2	18.0	18.7	19.4	19.8	20.2	20.9	21.6	22.4	23.1
95°	32.4	33.3	34.1	35.0	35.9	36.3	36.8	37.8	38.7	39.7	40.7
97.5°	53.3	53.9	54.5	55.2	55.8	56.1	56.5	57.2	57.9	58.7	59.4
100°	74.7	75.4	76.2	76.9	77.6	78.0	78.3	78.9	79.6	80.2	80.8
102.5°	99.5	99.9	100.2	100.6	100.9	101.1	101.5	102.4	103.3	104.1	105.0
105°	123.7	123.9	124.2	124.4	124.7	124.8	125.3	126.4	127.5	128.6	129.7
107.5°	152.2	152.3	152.5	152.6	152.7	152.8	153.0	153.5	154.0	154.5	155.0
110°	178.6	178.8	179.1	179.3	179.6	179.7	179.8	180.1	180.3	180.6	180.8

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	206.1	206.2	206.3	206.4	206.5	206.6	206.6	206.6	206.6	206.6	206.6
115°	233.6	234.0	234.3	234.7	235.0	235.2	235.1	234.8	234.6	234.3	234.1
117.5°	261.6	261.7	261.9	262.0	262.1	262.2	262.1	261.8	261.6	261.3	261.1
120°	287.4	288.1	288.9	289.6	290.3	290.7	290.4	289.8	289.2	288.6	288.0
122.5°	314.4	314.9	315.4	315.9	316.4	316.6	316.5	316.2	316.0	315.7	315.5
125°	341.8	342.2	342.6	342.9	343.3	343.5	343.4	343.1	342.9	342.6	342.4
127.5°	367.1	367.8	368.6	369.3	370.0	370.4	370.3	370.0	369.8	369.5	369.3
130°	392.4	393.4	394.4	395.3	396.3	396.8	396.6	396.3	395.9	395.6	395.2
132.5°	417.7	418.7	419.7	420.6	421.6	422.1	422.0	421.7	421.5	421.2	421.0
135°	443.5	444.2	445.0	445.7	446.4	446.8	446.7	446.6	446.5	446.4	446.3
137.5°	467.1	467.7	468.3	469.0	469.6	469.9	470.1	470.4	470.8	471.1	471.5
140°	491.9	492.5	493.1	493.7	494.3	494.6	494.7	494.8	494.9	495.1	495.2
142.5°	514.4	515.0	515.6	516.3	516.9	517.2	517.3	517.6	517.8	518.1	518.3
145°	538.0	538.2	538.5	538.7	539.0	539.1	539.3	539.7	540.0	540.4	540.8
147.5°	558.4	558.9	559.4	559.9	560.4	560.6	560.8	561.1	561.5	561.8	562.2
150°	579.8	580.0	580.3	580.5	580.8	580.9	581.0	581.3	581.5	581.8	582.0
152.5°	597.4	597.8	598.1	598.5	598.8	599.0	599.1	599.2	599.3	599.5	599.6
155°	616.1	616.1	616.1	616.1	616.1	616.1	616.2	616.3	616.4	616.5	616.6
157.5°	632.0	631.9	631.8	631.7	631.6	631.5	631.6	631.7	631.8	631.9	632.0
160°	646.9	646.7	646.4	646.2	645.9	645.8	645.8	645.8	645.8	645.8	645.8
162.5°	660.1	659.7	659.3	659.0	658.6	658.4	658.5	658.6	658.7	658.9	659.0
165°	671.0	670.6	670.3	669.9	669.6	669.4	669.4	669.4	669.4	669.4	669.4
167.5°	680.4	679.9	679.4	678.9	678.4	678.2	678.3	678.4	678.5	678.6	678.7
170°	688.1	687.6	687.1	686.6	686.1	685.9	685.9	685.9	685.9	685.9	685.9
172.5°	694.1	693.6	693.1	692.6	692.1	691.9	691.9	691.9	691.9	691.9	691.9
175°	698.0	697.5	697.0	696.5	696.0	695.8	695.8	695.8	695.8	695.8	695.8
177.5°	700.2	699.7	699.2	698.7	698.2	698.0	698.0	698.0	698.0	698.0	698.0
180°	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	537.6	537.6	541.5	545.4	543.2	544.5	549.3	547.6	551.1	550.6	552.0
5°	578.1	582.9	586.8	595.1	596.4	595.1	603.4	605.6	609.5	604.7	606.9
7.5°	623.9	633.9	643.5	655.7	659.6	660.5	664.9	671.0	676.2	666.6	671.4
10°	668.4	683.6	703.2	714.1	723.7	727.2	730.7	734.6	740.7	746.4	742.0
12.5°	716.3	738.6	757.3	776.9	788.7	787.4	797.4	800.0	804.8	806.1	807.9
15°	755.6	786.9	798.7	827.9	830.5	839.3	850.6	860.6	861.9	859.3	859.3
17.5°	793.0	820.1	841.0	864.6	869.3	876.8	891.1	895.9	897.7	897.2	897.2
20°	823.6	841.4	876.8	896.4	904.2	913.8	923.8	929.9	931.3	933.0	930.4
22.5°	843.6	870.7	899.4	915.6	922.1	925.6	932.1	933.9	931.7	932.1	932.6
25°	859.3	885.9	903.4	907.7	907.3	902.9	898.1	889.8	889.0	885.5	878.5
27.5°	863.7	873.7	871.5	853.7	835.8	834.0	805.3	789.6	771.7	774.3	764.3
30°	840.1	827.1	796.1	750.8	732.0	701.5	669.2	635.7	622.6	608.2	634.8
32.5°	782.6	735.9	681.0	622.1	590.8	563.7	529.3	504.9	490.9	479.1	501.8
35°	695.8	623.0	550.2	494.4	468.7	444.3	412.0	399.8	382.4	384.1	386.3
37.5°	584.2	504.0	449.1	394.1	377.1	367.1	343.6	324.8	318.7	317.0	317.0
40°	479.6	413.7	364.9	321.8	308.7	300.4	281.6	272.9	266.4	264.6	266.8
42.5°	396.7	340.5	302.6	273.8	264.6	254.2	246.3	235.4	234.1	231.1	235.0
45°	333.1	284.3	255.9	235.0	227.1	223.2	214.5	208.0	205.3	204.9	208.0
47.5°	282.5	244.6	219.7	206.7	200.6	196.6	189.2	186.6	184.0	184.9	183.5
50°	237.2	208.8	192.7	180.9	177.0	173.1	168.3	165.7	164.4	164.4	163.9
52.5°	203.6	180.1	169.6	158.7	157.0	154.8	149.5	147.8	145.6	145.2	146.9
55°	174.4	158.3	147.8	141.3	139.5	135.2	133.0	130.8	129.5	128.6	129.1
57.5°	149.1	136.9	129.9	124.3	121.2	119.5	115.5	115.1	114.2	114.2	113.8
60°	128.2	119.5	111.2	107.7	105.5	103.3	102.9	100.3	99.0	99.8	99.4
62.5°	108.6	101.6	96.8	92.9	91.6	89.8	88.5	87.6	86.3	86.8	86.8
65°	90.7	85.0	81.5	78.0	77.6	75.9	75.4	74.6	74.6	74.1	75.0
67.5°	74.6	70.6	67.6	65.4	64.1	64.5	62.8	61.5	61.5	61.0	62.3
70°	59.3	57.1	54.1	51.4	49.7	49.7	47.5	47.1	47.1	47.1	46.6
72.5°	45.8	41.9	40.5	39.7	39.7	39.7	38.8	38.8	38.4	38.8	38.4
75°	34.0	33.6	32.7	32.3	32.3	31.8	31.4	31.4	31.4	31.4	31.4
77.5°	26.6	26.6	25.7	25.3	25.3	25.3	24.9	24.9	24.4	24.4	24.4
80°	19.6	19.6	18.7	18.7	18.7	18.3	18.3	18.3	18.7	18.3	18.3
82.5°	13.5	13.5	13.1	13.5	13.1	12.6	12.6	12.6	12.2	12.6	12.6
85°	7.8	7.8	7.4	7.0	7.4	7.4	7.0	7.4	7.0	7.4	7.0
87.5°	3.1	2.6	2.6	2.6	2.2	2.6	2.2	2.2	2.6	2.2	2.6
90°	13.7	14.2	14.7	15.2	15.4	15.5	15.8	16.0	16.3	16.5	16.3
92.5°	23.5	23.8	24.2	24.5	24.7	24.6	24.3	24.1	23.8	23.6	23.8
95°	41.2	41.7	42.2	42.7	42.9	42.9	42.9	42.9	42.9	42.9	42.9
97.5°	60.0	60.6	61.2	61.8	62.1	62.0	61.9	61.8	61.7	61.6	61.7
100°	81.2	81.5	81.9	82.2	82.4	82.5	82.8	83.0	83.3	83.5	83.3
102.5°	105.4	105.7	106.1	106.4	106.6	106.5	106.4	106.3	106.2	106.1	106.2
105°	129.7	129.7	129.7	129.7	129.7	129.8	130.1	130.3	130.6	130.8	130.6
107.5°	155.4	155.7	156.1	156.4	156.6	156.5	156.4	156.3	156.2	156.1	156.2
110°	181.3	181.8	182.3	182.8	183.0	182.9	182.6	182.4	182.1	181.9	182.1

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	207.2	207.8	208.5	209.1	209.4	209.4	209.4	209.4	209.4	209.4	209.4
115°	234.2	234.4	234.5	234.6	234.7	234.6	234.5	234.4	234.2	234.1	234.2
117.5°	261.1	261.1	261.1	261.1	261.1	260.9	260.5	260.2	259.8	259.4	259.8
120°	287.9	287.7	287.6	287.5	287.4	287.3	287.0	286.8	286.5	286.3	286.5
122.5°	315.1	314.7	314.4	314.0	313.8	313.6	313.3	312.9	312.6	312.2	312.6
125°	341.9	341.4	340.9	340.4	340.2	340.0	339.5	339.0	338.5	338.0	338.5
127.5°	368.6	367.8	367.1	366.4	366.0	365.8	365.3	364.8	364.3	363.8	364.3
130°	394.7	394.2	393.7	393.2	393.0	392.6	391.7	390.8	390.0	389.1	390.0
132.5°	420.4	419.8	419.1	418.5	418.2	417.9	417.3	416.7	416.1	415.5	416.1
135°	445.8	445.3	444.8	444.3	444.1	444.0	443.7	443.5	443.2	443.0	443.2
137.5°	470.9	470.3	469.7	469.1	468.8	468.6	468.2	467.9	467.5	467.1	467.5
140°	495.1	494.9	494.8	494.7	494.6	494.2	493.3	492.5	491.6	490.8	491.6
142.5°	518.2	518.0	517.9	517.8	517.7	517.4	516.8	516.2	515.6	515.0	515.6
145°	540.7	540.5	540.4	540.3	540.2	540.0	539.5	539.0	538.5	538.0	538.5
147.5°	562.2	562.2	562.2	562.2	562.2	561.8	561.1	560.4	559.6	558.9	559.6
150°	582.0	582.0	582.0	582.0	582.0	581.6	580.9	580.2	579.4	578.7	579.4
152.5°	599.8	600.1	600.3	600.6	600.7	600.4	599.8	599.1	598.5	597.9	598.5
155°	617.1	617.6	618.1	618.6	618.8	618.4	617.5	616.7	615.8	615.0	615.8
157.5°	632.5	633.0	633.5	634.0	634.2	633.8	633.1	632.4	631.6	630.9	631.6
160°	646.4	647.0	647.6	648.2	648.5	648.3	647.8	647.3	646.8	646.3	646.8
162.5°	659.6	660.2	660.8	661.4	661.7	661.3	660.4	659.6	658.7	657.9	658.7
165°	670.1	670.9	671.6	672.3	672.7	672.3	671.4	670.5	669.7	668.8	669.7
167.5°	679.4	680.2	680.9	681.6	682.0	681.6	680.9	680.2	679.4	678.7	679.4
170°	686.7	687.6	688.4	689.3	689.7	689.3	688.4	687.6	686.7	685.9	686.7
172.5°	692.6	693.4	694.1	694.8	695.2	694.8	693.9	693.1	692.2	691.4	692.2
175°	696.5	697.3	698.0	698.7	699.1	698.7	697.8	696.9	696.1	695.2	696.1
177.5°	698.7	699.5	700.2	700.9	701.3	700.9	700.0	699.1	698.3	697.4	698.3
180°	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	549.8	547.2	545.4	544.1	542.8	546.7	541.5	535.8	531.9	529.3	528.4
5°	607.3	601.7	596.9	592.9	593.8	593.8	584.7	574.6	565.9	561.1	555.9
7.5°	674.0	667.9	658.3	656.2	654.4	643.5	634.4	616.0	605.1	594.2	584.7
10°	740.3	732.4	723.3	720.2	715.9	702.4	688.4	664.9	651.4	631.3	618.7
12.5°	802.2	792.6	783.5	781.3	774.7	763.0	739.0	714.6	691.5	670.1	647.9
15°	854.1	851.5	837.5	828.8	814.4	798.3	793.0	759.9	730.7	708.5	668.4
17.5°	897.7	885.5	872.4	866.7	861.1	842.3	823.6	789.6	758.2	725.5	699.7
20°	932.6	919.0	909.9	901.6	899.0	877.6	848.0	817.9	783.5	746.8	713.3
22.5°	934.3	932.6	926.5	921.7	916.4	902.5	878.9	841.4	804.8	764.7	720.7
25°	898.1	895.5	912.9	908.6	912.1	906.8	894.2	862.8	820.1	773.0	728.5
27.5°	789.1	815.7	843.2	852.8	859.3	878.1	884.2	866.7	832.3	782.1	732.4
30°	640.9	676.2	720.7	744.7	763.0	797.8	843.2	848.9	832.7	792.6	731.6
32.5°	503.1	535.4	571.1	599.5	623.9	695.4	756.4	800.5	808.3	787.4	733.8
35°	405.5	419.4	453.4	480.5	513.6	574.6	646.6	717.6	765.6	768.2	727.2
37.5°	334.4	341.8	371.5	386.7	406.3	460.0	527.1	620.0	694.5	729.8	708.9
40°	276.8	293.9	310.9	319.6	333.5	370.6	435.1	507.9	600.3	665.7	680.6
42.5°	240.2	247.6	258.5	270.7	279.5	311.7	354.9	421.6	504.9	596.0	637.0
45°	211.9	214.5	225.8	233.7	242.8	265.5	296.0	351.8	425.1	514.9	584.7
47.5°	188.3	193.6	199.7	204.5	210.6	228.0	254.2	294.7	359.2	439.5	514.5
50°	167.4	170.5	178.3	180.5	184.9	197.1	217.1	248.1	301.3	365.4	443.0
52.5°	147.8	153.5	156.5	159.6	163.5	173.5	186.6	211.9	252.0	312.2	378.0
55°	132.5	134.3	138.6	141.3	144.3	151.3	162.6	181.4	212.8	260.7	323.1
57.5°	117.7	117.7	122.1	124.3	127.3	132.5	142.6	157.0	179.6	215.4	272.5
60°	102.0	102.5	105.9	108.6	109.4	114.7	122.9	134.3	151.7	177.9	224.5
62.5°	88.1	90.2	92.0	92.9	95.9	99.0	105.9	113.8	126.0	149.1	182.2
65°	76.3	76.7	78.0	78.9	80.2	83.7	88.9	94.2	104.6	121.6	148.7
67.5°	62.8	64.5	66.3	66.3	67.6	69.3	74.6	78.9	86.8	96.8	115.1
70°	47.1	48.0	50.6	51.9	53.6	56.7	59.3	61.9	68.0	75.4	89.4
72.5°	39.2	39.2	40.1	40.5	40.5	42.7	46.6	49.3	52.3	57.5	67.1
75°	31.4	31.4	32.7	32.3	33.1	34.0	34.4	36.2	37.9	41.9	47.5
77.5°	24.9	25.3	25.3	25.7	25.7	26.2	26.6	27.5	28.3	30.5	33.1
80°	18.3	18.7	18.7	19.2	19.2	19.6	20.1	20.5	21.4	22.2	23.5
82.5°	12.6	13.1	13.1	13.5	13.1	13.5	14.0	14.0	14.4	15.3	15.7
85°	7.4	7.4	7.8	7.4	7.4	7.4	7.8	7.8	8.3	9.6	9.6
87.5°	2.2	2.6	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.5	3.9
90°	16.0	15.8	15.5	15.4	15.2	14.7	14.2	13.7	13.2	11.6	10.0
92.5°	24.1	24.3	24.6	24.7	24.5	24.2	23.8	23.5	23.1	22.4	21.6
95°	42.9	42.9	42.9	42.9	42.7	42.2	41.7	41.2	40.7	39.7	38.7
97.5°	61.8	61.9	62.0	62.1	61.8	61.2	60.6	60.0	59.4	58.7	57.9
100°	83.0	82.8	82.5	82.4	82.2	81.9	81.5	81.2	80.8	80.2	79.6
102.5°	106.3	106.4	106.5	106.6	106.4	106.1	105.7	105.4	105.0	104.1	103.3
105°	130.3	130.1	129.8	129.7	129.7	129.7	129.7	129.7	129.7	128.6	127.5
107.5°	156.3	156.4	156.5	156.6	156.4	156.1	155.7	155.4	155.0	154.5	154.0
110°	182.4	182.6	182.9	183.0	182.8	182.3	181.8	181.3	180.8	180.6	180.3

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	209.4	209.4	209.4	209.4	209.1	208.5	207.8	207.2	206.6	206.6	206.6
115°	234.4	234.5	234.6	234.7	234.6	234.5	234.4	234.2	234.1	234.3	234.6
117.5°	260.2	260.5	260.9	261.1	261.1	261.1	261.1	261.1	261.1	261.3	261.6
120°	286.8	287.0	287.3	287.4	287.5	287.6	287.7	287.9	288.0	288.6	289.2
122.5°	312.9	313.3	313.6	313.8	314.0	314.4	314.7	315.1	315.5	315.7	316.0
125°	339.0	339.5	340.0	340.2	340.4	340.9	341.4	341.9	342.4	342.6	342.9
127.5°	364.8	365.3	365.8	366.0	366.4	367.1	367.8	368.6	369.3	369.5	369.8
130°	390.8	391.7	392.6	393.0	393.2	393.7	394.2	394.7	395.2	395.6	395.9
132.5°	416.7	417.3	417.9	418.2	418.5	419.1	419.8	420.4	421.0	421.2	421.5
135°	443.5	443.7	444.0	444.1	444.3	444.8	445.3	445.8	446.3	446.4	446.5
137.5°	467.9	468.2	468.6	468.8	469.1	469.7	470.3	470.9	471.5	471.1	470.8
140°	492.5	493.3	494.2	494.6	494.7	494.8	494.9	495.1	495.2	495.1	494.9
142.5°	516.2	516.8	517.4	517.7	517.8	517.9	518.0	518.2	518.3	518.1	517.8
145°	539.0	539.5	540.0	540.2	540.3	540.4	540.5	540.7	540.8	540.4	540.0
147.5°	560.4	561.1	561.8	562.2	562.2	562.2	562.2	562.2	562.2	561.8	561.5
150°	580.2	580.9	581.6	582.0	582.0	582.0	582.0	582.0	582.0	581.8	581.5
152.5°	599.1	599.8	600.4	600.7	600.6	600.3	600.1	599.8	599.6	599.5	599.3
155°	616.7	617.5	618.4	618.8	618.6	618.1	617.6	617.1	616.6	616.5	616.4
157.5°	632.4	633.1	633.8	634.2	634.0	633.5	633.0	632.5	632.0	631.9	631.8
160°	647.3	647.8	648.3	648.5	648.2	647.6	647.0	646.4	645.8	645.8	645.8
162.5°	659.6	660.4	661.3	661.7	661.4	660.8	660.2	659.6	659.0	658.9	658.7
165°	670.5	671.4	672.3	672.7	672.3	671.6	670.9	670.1	669.4	669.4	669.4
167.5°	680.2	680.9	681.6	682.0	681.6	680.9	680.2	679.4	678.7	678.6	678.5
170°	687.6	688.4	689.3	689.7	689.3	688.4	687.6	686.7	685.9	685.9	685.9
172.5°	693.1	693.9	694.8	695.2	694.8	694.1	693.4	692.6	691.9	691.9	691.9
175°	696.9	697.8	698.7	699.1	698.7	698.0	697.3	696.5	695.8	695.8	695.8
177.5°	699.1	700.0	700.9	701.3	700.9	700.2	699.5	698.7	698.0	698.0	698.0
180°	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	527.1	524.9	522.7	522.7	517.9	513.6	511.4	512.3	509.7	506.2	502.7
5°	550.2	541.5	539.7	534.9	528.4	519.3	514.5	510.1	504.9	497.9	491.4
7.5°	571.6	560.2	554.1	549.3	536.7	524.0	513.6	506.6	497.5	487.0	479.1
10°	599.5	578.5	572.0	561.1	543.2	525.4	513.1	501.8	489.2	477.0	466.5
12.5°	621.7	597.7	585.5	574.6	551.5	528.8	508.4	494.4	479.1	465.6	452.1
15°	647.0	620.0	598.6	585.5	556.3	528.8	505.7	486.1	469.1	452.5	440.8
17.5°	659.2	625.2	615.6	596.9	554.6	527.1	498.8	477.8	457.3	438.2	424.2
20°	678.4	638.7	614.7	602.1	564.6	524.0	490.9	466.9	445.6	425.1	410.3
22.5°	679.7	636.5	620.8	596.9	550.6	514.9	483.9	454.7	429.9	410.7	395.4
25°	676.6	632.6	610.8	591.6	553.3	509.7	470.0	441.2	416.8	394.6	376.7
27.5°	675.3	621.3	600.8	581.6	538.4	494.4	461.7	429.0	401.1	381.5	363.2
30°	673.6	609.1	584.2	562.0	522.3	482.6	443.4	415.1	388.5	363.6	345.3
32.5°	662.3	592.5	567.2	543.7	500.9	461.3	430.3	400.2	371.5	348.3	331.8
35°	658.8	577.2	544.1	518.8	477.0	441.6	409.0	384.1	357.1	334.0	314.3
37.5°	648.7	561.5	525.8	493.5	449.9	416.4	392.4	367.5	341.4	316.5	300.8
40°	631.3	543.2	502.7	469.6	424.6	390.6	368.4	350.1	324.4	302.1	283.0
42.5°	605.6	524.5	480.9	446.0	396.3	364.5	346.2	328.7	306.9	283.8	268.1
45°	575.9	499.6	459.1	420.3	369.7	338.8	319.6	309.1	289.1	269.4	251.1
47.5°	535.4	473.9	433.8	393.7	342.2	312.2	296.9	286.4	272.5	251.1	236.3
50°	484.4	440.8	402.8	367.1	315.2	286.4	271.2	263.3	251.6	236.3	221.9
52.5°	427.7	402.4	371.0	337.9	287.7	260.7	246.8	240.7	231.9	217.6	205.3
55°	370.6	359.7	338.3	305.6	259.0	236.7	224.5	216.7	210.1	199.7	189.2
57.5°	319.6	314.3	299.5	274.2	235.0	211.9	201.4	196.2	191.0	183.1	172.6
60°	266.8	272.5	257.2	244.6	208.8	188.8	179.6	174.0	171.3	164.4	157.8
62.5°	221.0	226.3	217.6	208.0	182.7	164.8	159.1	153.9	152.2	146.1	139.5
65°	179.6	186.2	179.6	174.4	159.1	144.3	137.3	134.7	133.0	129.1	123.8
67.5°	143.0	149.5	146.5	139.9	135.2	122.9	119.0	116.4	115.5	112.5	108.1
70°	107.7	116.8	117.7	113.8	109.4	103.8	101.1	100.3	98.1	95.5	92.9
72.5°	77.6	88.1	88.5	88.5	85.9	85.9	83.3	82.0	82.0	79.3	76.3
75°	57.1	64.1	65.0	65.8	67.1	68.4	66.7	66.7	66.3	63.7	62.3
77.5°	37.9	44.0	46.2	49.3	51.0	51.0	51.9	52.8	51.9	50.6	49.7
80°	24.4	28.8	31.4	33.1	35.8	37.1	38.4	38.8	37.9	37.5	36.2
82.5°	16.1	17.4	18.7	20.9	24.0	26.2	26.2	25.7	26.6	26.2	25.7
85°	9.2	10.0	10.5	10.9	12.6	14.8	15.3	15.7	16.6	15.7	14.8
87.5°	3.5	3.9	3.9	3.9	4.8	5.2	6.5	8.3	7.8	7.0	7.0
90°	8.4	6.8	6.0	5.4	4.2	2.9	1.7	0.5	1.7	2.9	4.2
92.5°	20.9	20.2	19.8	19.4	18.7	18.0	17.2	16.5	17.2	18.0	18.7
95°	37.8	36.8	36.3	35.9	35.0	34.1	33.3	32.4	33.3	34.1	35.0
97.5°	57.2	56.5	56.1	55.8	55.2	54.5	53.9	53.3	53.9	54.5	55.2
100°	78.9	78.3	78.0	77.6	76.9	76.2	75.4	74.7	75.4	76.2	76.9
102.5°	102.4	101.5	101.1	100.9	100.6	100.2	99.9	99.5	99.9	100.2	100.6
105°	126.4	125.3	124.8	124.7	124.4	124.2	123.9	123.7	123.9	124.2	124.4
107.5°	153.5	153.0	152.8	152.7	152.6	152.5	152.3	152.2	152.3	152.5	152.6
110°	180.1	179.8	179.7	179.6	179.3	179.1	178.8	178.6	178.8	179.1	179.3

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	206.6	206.6	206.6	206.5	206.4	206.3	206.2	206.1	206.2	206.3	206.4
115°	234.8	235.1	235.2	235.0	234.7	234.3	234.0	233.6	234.0	234.3	234.7
117.5°	261.8	262.1	262.2	262.1	262.0	261.9	261.7	261.6	261.7	261.9	262.0
120°	289.8	290.4	290.7	290.3	289.6	288.9	288.1	287.4	288.1	288.9	289.6
122.5°	316.2	316.5	316.6	316.4	315.9	315.4	314.9	314.4	314.9	315.4	315.9
125°	343.1	343.4	343.5	343.3	342.9	342.6	342.2	341.8	342.2	342.6	342.9
127.5°	370.0	370.3	370.4	370.0	369.3	368.6	367.8	367.1	367.8	368.6	369.3
130°	396.3	396.6	396.8	396.3	395.3	394.4	393.4	392.4	393.4	394.4	395.3
132.5°	421.7	422.0	422.1	421.6	420.6	419.7	418.7	417.7	418.7	419.7	420.6
135°	446.6	446.7	446.8	446.4	445.7	445.0	444.2	443.5	444.2	445.0	445.7
137.5°	470.4	470.1	469.9	469.6	469.0	468.3	467.7	467.1	467.7	468.3	469.0
140°	494.8	494.7	494.6	494.3	493.7	493.1	492.5	491.9	492.5	493.1	493.7
142.5°	517.6	517.3	517.2	516.9	516.3	515.6	515.0	514.4	515.0	515.6	516.3
145°	539.7	539.3	539.1	539.0	538.7	538.5	538.2	538.0	538.2	538.5	538.7
147.5°	561.1	560.8	560.6	560.4	559.9	559.4	558.9	558.4	558.9	559.4	559.9
150°	581.3	581.0	580.9	580.8	580.5	580.3	580.0	579.8	580.0	580.3	580.5
152.5°	599.2	599.1	599.0	598.8	598.5	598.1	597.8	597.4	597.8	598.1	598.5
155°	616.3	616.2	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
157.5°	631.7	631.6	631.5	631.6	631.7	631.8	631.9	632.0	631.9	631.8	631.7
160°	645.8	645.8	645.8	645.9	646.2	646.4	646.7	646.9	646.7	646.4	646.2
162.5°	658.6	658.5	658.4	658.6	659.0	659.3	659.7	660.1	659.7	659.3	659.0
165°	669.4	669.4	669.4	669.6	669.9	670.3	670.6	671.0	670.6	670.3	669.9
167.5°	678.4	678.3	678.2	678.4	678.9	679.4	679.9	680.4	679.9	679.4	678.9
170°	685.9	685.9	685.9	686.1	686.6	687.1	687.6	688.1	687.6	687.1	686.6
172.5°	691.9	691.9	691.9	692.1	692.6	693.1	693.6	694.1	693.6	693.1	692.6
175°	695.8	695.8	695.8	696.0	696.5	697.0	697.5	698.0	697.5	697.0	696.5
177.5°	698.0	698.0	698.0	698.2	698.7	699.2	699.7	700.2	699.7	699.2	698.7
180°	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	502.7	500.5	499.6	497.5	492.2	488.7	484.8	482.2	482.6	480.5	481.8
5°	487.0	486.6	483.5	479.1	471.7	467.8	460.8	457.3	455.6	456.0	453.4
7.5°	473.9	470.0	467.8	460.8	453.9	445.6	439.9	436.9	434.2	431.6	429.9
10°	459.1	455.6	452.1	444.7	435.1	427.3	419.4	416.4	412.4	410.7	409.4
12.5°	443.4	441.2	436.9	428.1	417.2	409.8	400.7	398.9	393.7	390.2	389.3
15°	429.0	427.7	419.8	409.8	398.9	391.5	383.7	378.4	369.7	371.5	368.4
17.5°	413.7	408.1	403.3	389.8	384.5	373.2	364.0	361.4	355.3	351.4	347.5
20°	396.7	393.3	387.2	378.4	365.8	352.7	345.7	341.4	337.9	331.8	330.0
22.5°	380.6	376.3	371.0	359.7	348.8	337.9	328.3	324.4	320.0	315.7	313.0
25°	368.0	361.4	355.8	341.8	330.9	321.8	315.7	309.1	303.0	300.4	299.5
27.5°	348.3	344.4	338.8	325.7	315.7	305.6	300.0	295.6	289.1	286.0	283.4
30°	335.7	327.9	321.3	310.9	300.8	289.9	284.7	279.5	275.5	271.6	268.6
32.5°	318.7	312.6	307.4	296.9	286.9	276.8	271.2	263.3	261.2	258.1	254.6
35°	302.1	298.2	292.5	281.2	270.3	263.3	257.2	249.8	247.2	245.0	242.0
37.5°	286.4	280.8	276.8	265.9	256.4	248.1	243.3	237.2	235.4	232.8	230.6
40°	272.9	267.3	263.3	252.4	242.4	233.7	230.6	224.5	221.9	218.9	217.6
42.5°	257.7	252.9	247.6	239.8	229.3	220.6	214.5	211.0	207.5	206.2	203.6
45°	241.5	237.2	233.2	224.5	213.6	207.5	202.3	197.5	194.9	192.7	191.0
47.5°	227.6	223.7	218.4	208.8	200.1	194.4	189.2	184.4	181.8	179.2	177.0
50°	211.5	209.3	203.6	194.4	186.2	179.6	174.8	170.5	168.7	165.7	162.2
52.5°	197.1	193.1	188.3	180.9	173.5	165.7	159.1	156.5	153.5	151.7	148.7
55°	180.1	177.4	172.2	165.7	157.8	151.3	146.5	143.0	139.1	137.3	133.4
57.5°	165.7	160.9	158.3	150.0	142.6	136.0	132.5	129.1	124.7	122.1	120.3
60°	150.0	145.6	141.7	134.7	129.5	122.5	117.3	114.2	111.2	107.7	105.9
62.5°	134.7	131.2	126.4	120.8	114.2	108.6	104.6	100.3	98.5	95.0	93.7
65°	118.2	115.5	111.6	105.1	99.8	95.0	91.1	87.6	85.9	84.6	83.7
67.5°	103.3	99.8	97.2	91.6	85.9	82.0	79.8	77.6	75.4	74.1	72.8
70°	88.1	85.5	82.8	77.6	73.7	70.2	68.4	66.7	65.4	64.1	62.8
72.5°	72.4	71.1	68.4	65.0	61.9	59.3	58.0	55.8	54.5	52.3	51.4
75°	59.7	57.5	56.2	53.2	50.6	48.4	46.6	44.0	42.3	41.4	41.0
77.5°	47.1	46.2	44.5	41.9	40.5	38.4	35.8	34.9	34.0	34.0	33.6
80°	35.3	34.0	32.7	30.5	29.2	27.5	27.5	27.5	27.0	27.5	27.0
82.5°	24.0	23.1	22.2	20.9	20.5	20.5	20.9	20.9	20.9	20.9	20.9
85°	14.0	14.0	14.0	14.4	14.0	14.0	14.4	14.8	14.4	14.4	14.0
87.5°	6.5	6.5	7.0	7.0	7.4	7.4	7.4	7.4	7.4	7.4	7.8
90°	5.4	6.0	6.8	8.4	10.0	11.6	13.2	13.7	14.2	14.7	15.2
92.5°	19.4	19.8	20.2	20.9	21.6	22.4	23.1	23.5	23.8	24.2	24.5
95°	35.9	36.3	36.8	37.8	38.7	39.7	40.7	41.2	41.7	42.2	42.7
97.5°	55.8	56.1	56.5	57.2	57.9	58.7	59.4	60.0	60.6	61.2	61.8
100°	77.6	78.0	78.3	78.9	79.6	80.2	80.8	81.2	81.5	81.9	82.2
102.5°	100.9	101.1	101.5	102.4	103.3	104.1	105.0	105.4	105.7	106.1	106.4
105°	124.7	124.8	125.3	126.4	127.5	128.6	129.7	129.7	129.7	129.7	129.7
107.5°	152.7	152.8	153.0	153.5	154.0	154.5	155.0	155.4	155.7	156.1	156.4
110°	179.6	179.7	179.8	180.1	180.3	180.6	180.8	181.3	181.8	182.3	182.8

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	206.5	206.6	206.6	206.6	206.6	206.6	206.6	207.2	207.8	208.5	209.1
115°	235.0	235.2	235.1	234.8	234.6	234.3	234.1	234.2	234.4	234.5	234.6
117.5°	262.1	262.2	262.1	261.8	261.6	261.3	261.1	261.1	261.1	261.1	261.1
120°	290.3	290.7	290.4	289.8	289.2	288.6	288.0	287.9	287.7	287.6	287.5
122.5°	316.4	316.6	316.5	316.2	316.0	315.7	315.5	315.1	314.7	314.4	314.0
125°	343.3	343.5	343.4	343.1	342.9	342.6	342.4	341.9	341.4	340.9	340.4
127.5°	370.0	370.4	370.3	370.0	369.8	369.5	369.3	368.6	367.8	367.1	366.4
130°	396.3	396.8	396.6	396.3	395.9	395.6	395.2	394.7	394.2	393.7	393.2
132.5°	421.6	422.1	422.0	421.7	421.5	421.2	421.0	420.4	419.8	419.1	418.5
135°	446.4	446.8	446.7	446.6	446.5	446.4	446.3	445.8	445.3	444.8	444.3
137.5°	469.6	469.9	470.1	470.4	470.8	471.1	471.5	470.9	470.3	469.7	469.1
140°	494.3	494.6	494.7	494.8	494.9	495.1	495.2	495.1	494.9	494.8	494.7
142.5°	516.9	517.2	517.3	517.6	517.8	518.1	518.3	518.2	518.0	517.9	517.8
145°	539.0	539.1	539.3	539.7	540.0	540.4	540.8	540.7	540.5	540.4	540.3
147.5°	560.4	560.6	560.8	561.1	561.5	561.8	562.2	562.2	562.2	562.2	562.2
150°	580.8	580.9	581.0	581.3	581.5	581.8	582.0	582.0	582.0	582.0	582.0
152.5°	598.8	599.0	599.1	599.2	599.3	599.5	599.6	599.8	600.1	600.3	600.6
155°	616.1	616.1	616.2	616.3	616.4	616.5	616.6	617.1	617.6	618.1	618.6
157.5°	631.6	631.5	631.6	631.7	631.8	631.9	632.0	632.5	633.0	633.5	634.0
160°	645.9	645.8	645.8	645.8	645.8	645.8	645.8	646.4	647.0	647.6	648.2
162.5°	658.6	658.4	658.5	658.6	658.7	658.9	659.0	659.6	660.2	660.8	661.4
165°	669.6	669.4	669.4	669.4	669.4	669.4	669.4	670.1	670.9	671.6	672.3
167.5°	678.4	678.2	678.3	678.4	678.5	678.6	678.7	679.4	680.2	680.9	681.6
170°	686.1	685.9	685.9	685.9	685.9	685.9	685.9	686.7	687.6	688.4	689.3
172.5°	692.1	691.9	691.9	691.9	691.9	691.9	691.9	692.6	693.4	694.1	694.8
175°	696.0	695.8	695.8	695.8	695.8	695.8	695.8	696.5	697.3	698.0	698.7
177.5°	698.2	698.0	698.0	698.0	698.0	698.0	698.0	698.7	699.5	700.2	700.9
180°	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	481.3	481.8	480.5	477.8	477.4	478.3	480.9	480.0	477.8	481.8	478.3
5°	454.7	452.5	451.7	452.5	449.9	448.6	451.2	449.9	451.2	451.7	453.0
7.5°	429.0	429.4	426.8	427.3	423.8	424.6	424.6	424.6	426.0	426.8	428.6
10°	406.8	407.6	404.6	405.0	402.4	400.7	402.0	404.6	404.6	404.6	405.5
12.5°	388.9	385.0	382.8	382.4	379.3	378.4	381.0	381.9	384.1	384.1	385.4
15°	366.7	365.8	364.0	364.0	356.6	358.4	359.2	362.3	366.7	363.2	364.0
17.5°	346.6	344.4	342.2	341.4	340.5	337.9	341.4	340.9	343.6	344.0	345.3
20°	328.7	327.0	322.6	323.1	323.9	320.0	322.2	322.2	324.8	327.4	330.5
22.5°	311.3	309.5	307.4	308.2	305.6	304.8	304.8	306.9	310.0	312.2	311.7
25°	297.8	294.7	293.4	292.1	290.8	291.7	290.4	292.5	294.7	296.0	294.7
27.5°	282.5	281.2	278.6	277.3	275.1	276.0	276.8	278.6	279.9	279.9	281.2
30°	267.7	265.9	265.1	263.8	263.8	262.0	262.5	264.2	265.5	266.8	268.6
32.5°	253.3	252.0	250.7	250.7	249.8	249.4	248.9	251.6	251.6	254.2	254.2
35°	241.5	239.4	239.4	237.2	238.0	237.6	236.7	238.5	238.9	240.7	240.2
37.5°	228.5	228.5	227.6	225.4	223.7	224.1	226.3	226.3	227.6	227.1	228.5
40°	215.4	214.5	214.5	213.2	212.8	212.3	212.8	213.2	215.4	214.9	215.4
42.5°	202.3	202.7	200.6	200.6	200.6	199.2	199.7	200.1	201.0	201.9	203.2
45°	189.7	188.8	188.3	187.5	186.6	187.0	186.6	188.3	187.9	188.8	190.1
47.5°	176.1	174.8	174.4	172.6	172.6	173.5	173.1	174.4	174.8	176.1	175.3
50°	163.1	161.3	160.0	160.4	157.8	158.7	158.7	160.0	161.3	161.7	162.6
52.5°	147.8	147.4	146.9	144.7	144.3	143.9	144.3	144.7	146.5	147.8	148.2
55°	133.0	132.5	129.9	129.1	127.7	127.7	128.6	129.1	132.1	132.5	134.3
57.5°	119.5	118.2	115.1	114.7	114.7	114.7	113.4	115.1	116.0	118.2	118.2
60°	104.6	104.6	102.0	102.0	102.5	102.0	102.0	102.5	102.5	104.2	105.1
62.5°	92.9	92.4	92.4	91.6	91.1	91.6	91.1	91.1	91.6	92.9	94.2
65°	82.4	82.0	81.5	81.1	80.2	80.2	80.7	81.5	81.5	82.4	82.8
67.5°	72.4	72.4	71.5	71.5	71.1	70.6	71.1	70.6	72.4	72.4	72.8
70°	62.3	61.9	60.6	60.2	58.9	59.3	59.3	60.6	61.0	61.9	62.8
72.5°	50.1	50.1	49.3	48.4	48.8	48.0	48.0	48.4	48.4	49.7	50.1
75°	41.4	40.5	40.1	40.5	40.1	41.0	40.1	40.1	41.0	41.0	41.0
77.5°	34.0	34.0	33.6	33.6	34.0	33.6	34.0	34.0	34.0	33.6	34.0
80°	27.9	27.5	27.5	27.5	27.0	27.0	27.0	27.0	27.0	27.0	27.0
82.5°	20.9	20.9	20.5	20.9	20.9	20.5	20.9	20.5	20.5	20.9	20.9
85°	14.0	14.8	14.0	14.0	14.4	14.4	14.8	14.4	14.8	14.0	14.4
87.5°	7.4	7.8	7.8	7.4	7.4	7.8	7.8	7.8	8.3	7.4	7.8
90°	15.4	15.5	15.8	16.0	16.3	16.5	16.3	16.0	15.8	15.5	15.4
92.5°	24.7	24.6	24.3	24.1	23.8	23.6	23.8	24.1	24.3	24.6	24.7
95°	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9	42.9
97.5°	62.1	62.0	61.9	61.8	61.7	61.6	61.7	61.8	61.9	62.0	62.1
100°	82.4	82.5	82.8	83.0	83.3	83.5	83.3	83.0	82.8	82.5	82.4
102.5°	106.6	106.5	106.4	106.3	106.2	106.1	106.2	106.3	106.4	106.5	106.6
105°	129.7	129.8	130.1	130.3	130.6	130.8	130.6	130.3	130.1	129.8	129.7
107.5°	156.6	156.5	156.4	156.3	156.2	156.1	156.2	156.3	156.4	156.5	156.6
110°	183.0	182.9	182.6	182.4	182.1	181.9	182.1	182.4	182.6	182.9	183.0

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	209.4	209.4	209.4	209.4	209.4	209.4	209.4	209.4	209.4	209.4	209.4
115°	234.7	234.6	234.5	234.4	234.2	234.1	234.2	234.4	234.5	234.6	234.7
117.5°	261.1	260.9	260.5	260.2	259.8	259.4	259.8	260.2	260.5	260.9	261.1
120°	287.4	287.3	287.0	286.8	286.5	286.3	286.5	286.8	287.0	287.3	287.4
122.5°	313.8	313.6	313.3	312.9	312.6	312.2	312.6	312.9	313.3	313.6	313.8
125°	340.2	340.0	339.5	339.0	338.5	338.0	338.5	339.0	339.5	340.0	340.2
127.5°	366.0	365.8	365.3	364.8	364.3	363.8	364.3	364.8	365.3	365.8	366.0
130°	393.0	392.6	391.7	390.8	390.0	389.1	390.0	390.8	391.7	392.6	393.0
132.5°	418.2	417.9	417.3	416.7	416.1	415.5	416.1	416.7	417.3	417.9	418.2
135°	444.1	444.0	443.7	443.5	443.2	443.0	443.2	443.5	443.7	444.0	444.1
137.5°	468.8	468.6	468.2	467.9	467.5	467.1	467.5	467.9	468.2	468.6	468.8
140°	494.6	494.2	493.3	492.5	491.6	490.8	491.6	492.5	493.3	494.2	494.6
142.5°	517.7	517.4	516.8	516.2	515.6	515.0	515.6	516.2	516.8	517.4	517.7
145°	540.2	540.0	539.5	539.0	538.5	538.0	538.5	539.0	539.5	540.0	540.2
147.5°	562.2	561.8	561.1	560.4	559.6	558.9	559.6	560.4	561.1	561.8	562.2
150°	582.0	581.6	580.9	580.2	579.4	578.7	579.4	580.2	580.9	581.6	582.0
152.5°	600.7	600.4	599.8	599.1	598.5	597.9	598.5	599.1	599.8	600.4	600.7
155°	618.8	618.4	617.5	616.7	615.8	615.0	615.8	616.7	617.5	618.4	618.8
157.5°	634.2	633.8	633.1	632.4	631.6	630.9	631.6	632.4	633.1	633.8	634.2
160°	648.5	648.3	647.8	647.3	646.8	646.3	646.8	647.3	647.8	648.3	648.5
162.5°	661.7	661.3	660.4	659.6	658.7	657.9	658.7	659.6	660.4	661.3	661.7
165°	672.7	672.3	671.4	670.5	669.7	668.8	669.7	670.5	671.4	672.3	672.7
167.5°	682.0	681.6	680.9	680.2	679.4	678.7	679.4	680.2	680.9	681.6	682.0
170°	689.7	689.3	688.4	687.6	686.7	685.9	686.7	687.6	688.4	689.3	689.7
172.5°	695.2	694.8	693.9	693.1	692.2	691.4	692.2	693.1	693.9	694.8	695.2
175°	699.1	698.7	697.8	696.9	696.1	695.2	696.1	696.9	697.8	698.7	699.1
177.5°	701.3	700.9	700.0	699.1	698.3	697.4	698.3	699.1	700.0	700.9	701.3
180°	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	481.8	483.5	481.8	478.3	481.8	483.9	486.1	489.6	491.4	491.4	494.0
5°	454.3	457.8	456.5	455.6	459.1	461.3	464.8	469.1	473.9	477.0	480.5
7.5°	429.9	432.1	434.2	434.2	437.7	442.5	447.8	453.0	459.1	463.4	466.1
10°	408.5	410.3	411.6	413.3	418.5	423.8	430.7	437.3	442.5	447.3	451.7
12.5°	388.0	390.6	393.7	395.0	398.9	405.5	412.0	419.8	428.1	432.9	437.3
15°	368.4	369.7	373.2	377.1	380.6	387.6	395.9	404.2	411.1	418.5	422.5
17.5°	348.3	348.8	357.9	355.8	367.1	373.6	378.0	385.8	397.2	403.3	409.4
20°	328.7	333.1	337.0	339.2	345.3	352.7	365.4	371.5	380.6	386.3	391.5
22.5°	313.5	320.0	320.0	325.2	328.3	335.3	344.4	356.2	366.2	370.1	377.6
25°	300.0	303.0	308.2	310.0	315.7	321.8	327.9	340.5	351.4	356.6	361.9
27.5°	282.5	286.4	293.4	293.4	300.8	307.4	314.8	323.1	334.0	341.4	347.0
30°	269.0	272.9	276.0	280.8	283.8	289.9	303.0	309.1	318.7	325.2	332.2
32.5°	256.4	259.4	262.0	267.3	270.7	277.7	284.7	295.6	303.9	310.0	317.4
35°	242.4	245.5	248.9	252.9	258.1	264.6	271.2	280.3	288.6	294.3	300.4
37.5°	229.3	231.5	236.7	239.4	243.7	249.8	258.1	267.7	275.1	279.5	285.6
40°	216.7	218.4	222.4	227.1	230.2	235.0	243.7	252.0	261.2	266.4	271.2
42.5°	203.2	205.3	208.8	213.6	218.4	223.7	228.5	238.0	246.3	250.7	255.9
45°	191.4	192.7	195.3	200.1	204.9	208.8	216.2	225.0	232.8	236.3	242.0
47.5°	177.4	178.8	182.7	184.9	190.1	195.3	202.7	211.5	218.4	221.9	227.1
50°	163.1	164.4	167.0	171.8	175.3	180.9	187.5	194.9	203.6	208.4	211.5
52.5°	149.1	151.7	153.9	157.8	162.2	167.9	174.0	180.9	188.3	193.1	196.6
55°	135.2	137.3	139.9	142.1	147.4	152.6	159.6	166.1	172.6	177.0	180.9
57.5°	119.5	122.5	125.1	129.5	133.4	137.8	145.6	150.8	158.7	161.7	165.2
60°	105.9	109.0	111.2	114.7	118.2	123.8	129.1	135.6	142.1	146.1	150.4
62.5°	94.6	95.9	97.2	100.7	104.2	109.4	114.7	121.2	128.2	130.4	133.8
65°	83.3	84.6	86.8	89.8	92.4	95.5	101.1	106.4	112.9	116.4	117.7
67.5°	73.7	75.0	75.4	77.6	79.8	83.3	86.3	91.6	97.7	99.8	102.5
70°	62.8	65.0	65.4	67.1	68.0	70.2	73.7	77.6	82.4	86.3	88.5
72.5°	50.1	53.2	54.1	56.7	58.0	60.2	62.8	65.8	68.9	70.6	72.4
75°	41.0	41.9	42.3	44.5	46.6	49.7	51.0	52.8	55.4	57.5	59.3
77.5°	34.0	34.4	34.9	34.9	35.3	37.1	39.7	41.9	43.6	44.5	45.8
80°	27.5	27.0	27.0	27.5	27.5	27.5	28.3	31.4	32.3	34.4	34.0
82.5°	21.4	20.5	20.9	20.5	20.5	20.5	20.5	20.9	20.9	22.2	23.1
85°	14.0	14.4	14.0	14.0	13.5	14.0	13.5	13.5	13.1	13.1	12.6
87.5°	7.4	7.8	7.4	7.4	7.0	7.4	7.0	7.0	6.5	6.5	5.7
90°	15.2	14.7	14.2	13.7	13.2	11.6	10.0	8.4	6.8	6.0	5.4
92.5°	24.5	24.2	23.8	23.5	23.1	22.4	21.6	20.9	20.2	19.8	19.4
95°	42.7	42.2	41.7	41.2	40.7	39.7	38.7	37.8	36.8	36.3	35.9
97.5°	61.8	61.2	60.6	60.0	59.4	58.7	57.9	57.2	56.5	56.1	55.8
100°	82.2	81.9	81.5	81.2	80.8	80.2	79.6	78.9	78.3	78.0	77.6
102.5°	106.4	106.1	105.7	105.4	105.0	104.1	103.3	102.4	101.5	101.1	100.9
105°	129.7	129.7	129.7	129.7	129.7	128.6	127.5	126.4	125.3	124.8	124.7
107.5°	156.4	156.1	155.7	155.4	155.0	154.5	154.0	153.5	153.0	152.8	152.7
110°	182.8	182.3	181.8	181.3	180.8	180.6	180.3	180.1	179.8	179.7	179.6

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	209.1	208.5	207.8	207.2	206.6	206.6	206.6	206.6	206.6	206.6	206.5
115°	234.6	234.5	234.4	234.2	234.1	234.3	234.6	234.8	235.1	235.2	235.0
117.5°	261.1	261.1	261.1	261.1	261.1	261.3	261.6	261.8	262.1	262.2	262.1
120°	287.5	287.6	287.7	287.9	288.0	288.6	289.2	289.8	290.4	290.7	290.3
122.5°	314.0	314.4	314.7	315.1	315.5	315.7	316.0	316.2	316.5	316.6	316.4
125°	340.4	340.9	341.4	341.9	342.4	342.6	342.9	343.1	343.4	343.5	343.3
127.5°	366.4	367.1	367.8	368.6	369.3	369.5	369.8	370.0	370.3	370.4	370.0
130°	393.2	393.7	394.2	394.7	395.2	395.6	395.9	396.3	396.6	396.8	396.3
132.5°	418.5	419.1	419.8	420.4	421.0	421.2	421.5	421.7	422.0	422.1	421.6
135°	444.3	444.8	445.3	445.8	446.3	446.4	446.5	446.6	446.7	446.8	446.4
137.5°	469.1	469.7	470.3	470.9	471.5	471.1	470.8	470.4	470.1	469.9	469.6
140°	494.7	494.8	494.9	495.1	495.2	495.1	494.9	494.8	494.7	494.6	494.3
142.5°	517.8	517.9	518.0	518.2	518.3	518.1	517.8	517.6	517.3	517.2	516.9
145°	540.3	540.4	540.5	540.7	540.8	540.4	540.0	539.7	539.3	539.1	539.0
147.5°	562.2	562.2	562.2	562.2	562.2	561.8	561.5	561.1	560.8	560.6	560.4
150°	582.0	582.0	582.0	582.0	582.0	581.8	581.5	581.3	581.0	580.9	580.8
152.5°	600.6	600.3	600.1	599.8	599.6	599.5	599.3	599.2	599.1	599.0	598.8
155°	618.6	618.1	617.6	617.1	616.6	616.5	616.4	616.3	616.2	616.1	616.1
157.5°	634.0	633.5	633.0	632.5	632.0	631.9	631.8	631.7	631.6	631.5	631.6
160°	648.2	647.6	647.0	646.4	645.8	645.8	645.8	645.8	645.8	645.8	645.9
162.5°	661.4	660.8	660.2	659.6	659.0	658.9	658.7	658.6	658.5	658.4	658.6
165°	672.3	671.6	670.9	670.1	669.4	669.4	669.4	669.4	669.4	669.4	669.6
167.5°	681.6	680.9	680.2	679.4	678.7	678.6	678.5	678.4	678.3	678.2	678.4
170°	689.3	688.4	687.6	686.7	685.9	685.9	685.9	685.9	685.9	685.9	686.1
172.5°	694.8	694.1	693.4	692.6	691.9	691.9	691.9	691.9	691.9	691.9	692.1
175°	698.7	698.0	697.3	696.5	695.8	695.8	695.8	695.8	695.8	695.8	696.0
177.5°	700.9	700.2	699.5	698.7	698.0	698.0	698.0	698.0	698.0	698.0	698.2
180°	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6	699.6

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	509.2	509.2	509.2	509.2
2.5°	496.1	499.2	505.3	510.5
5°	485.7	490.5	499.6	508.8
7.5°	473.0	480.5	492.2	504.9
10°	460.8	470.4	484.8	499.6
12.5°	448.6	458.7	473.9	493.1
15°	434.2	444.7	463.0	486.1
17.5°	421.6	435.5	452.1	475.2
20°	408.1	418.5	439.9	464.3
22.5°	391.1	408.5	428.6	454.3
25°	377.6	392.8	412.9	442.1
27.5°	361.0	378.9	403.3	429.0
30°	347.5	362.3	385.0	415.9
32.5°	331.8	349.2	372.8	403.3
35°	317.8	332.7	354.9	385.8
37.5°	301.3	317.4	342.2	369.7
40°	286.9	302.6	326.1	351.8
42.5°	269.4	286.0	309.5	331.3
45°	255.5	270.7	289.5	309.5
47.5°	238.5	254.6	272.9	286.9
50°	223.2	238.0	252.4	264.2
52.5°	206.7	220.2	233.2	242.0
55°	191.4	201.9	212.3	218.4
57.5°	173.5	183.5	192.3	195.8
60°	157.8	166.1	171.8	175.7
62.5°	141.3	147.4	151.7	153.9
65°	125.1	129.5	131.7	133.8
67.5°	108.6	112.5	113.8	116.4
70°	91.1	95.5	96.4	97.7
72.5°	78.0	78.0	79.8	81.5
75°	62.3	63.2	64.1	64.1
77.5°	48.8	48.8	49.7	50.1
80°	35.8	36.2	36.2	35.8
82.5°	24.4	25.3	24.4	24.0
85°	13.5	15.3	14.4	14.4
87.5°	5.7	5.7	6.5	5.7
90°	4.2	2.9	1.7	0.5
92.5°	18.7	18.0	17.2	16.5
95°	35.0	34.1	33.3	32.4
97.5°	55.2	54.5	53.9	53.3
100°	76.9	76.2	75.4	74.7
102.5°	100.6	100.2	99.9	99.5
105°	124.4	124.2	123.9	123.7
107.5°	152.6	152.5	152.3	152.2
110°	179.3	179.1	178.8	178.6

TEST NUMBER: P1012519

CATALOG NUMBER: S123RDIP-B340D585UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	206.4	206.3	206.2	206.1
115°	234.7	234.3	234.0	233.6
117.5°	262.0	261.9	261.7	261.6
120°	289.6	288.9	288.1	287.4
122.5°	315.9	315.4	314.9	314.4
125°	342.9	342.6	342.2	341.8
127.5°	369.3	368.6	367.8	367.1
130°	395.3	394.4	393.4	392.4
132.5°	420.6	419.7	418.7	417.7
135°	445.7	445.0	444.2	443.5
137.5°	469.0	468.3	467.7	467.1
140°	493.7	493.1	492.5	491.9
142.5°	516.3	515.6	515.0	514.4
145°	538.7	538.5	538.2	538.0
147.5°	559.9	559.4	558.9	558.4
150°	580.5	580.3	580.0	579.8
152.5°	598.5	598.1	597.8	597.4
155°	616.1	616.1	616.1	616.1
157.5°	631.7	631.8	631.9	632.0
160°	646.2	646.4	646.7	646.9
162.5°	659.0	659.3	659.7	660.1
165°	669.9	670.3	670.6	671.0
167.5°	678.9	679.4	679.9	680.4
170°	686.6	687.1	687.6	688.1
172.5°	692.6	693.1	693.6	694.1
175°	696.5	697.0	697.5	698.0
177.5°	698.7	699.2	699.7	700.2
180°	699.6	699.6	699.6	699.6

(END OF REPORT)