

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012532

Luminaire Tested: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012532
REPORT IS A COMBINATION OF REPORTS P993297 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D805UB30-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4158.0 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32	32	32	32			
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34	27	27	27	27			
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	30	29	24	24	24	24			
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	28	27	25	20	20	20	20			
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	25	24	22	18	18	18	18			
5	66	55	47	42	59	50	43	38	40	36	32	31	28	26	23	21	19	16	16	16	16			
6	61	49	42	36	55	45	38	33	36	32	28	28	25	22	21	19	17	14	14	14	14			
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15	13	13	13	13			
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11	11	11	11			
9	49	37	30	25	44	34	27	23	28	23	20	22	18	16	16	14	12	10	10	10	10			
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11	9	9	9	9			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5702	5702	5702	5702
5°	5707	6567	5721	4872
10°	5655	7927	5680	4255
15°	5598	8997	5598	3752
20°	5483	9704	5513	3329
25°	5399	9220	5389	3037
30°	5302	6389	5289	2753
35°	5184	4101	5159	2538
40°	5037	2896	5012	2324
45°	4782	2318	4775	2116
50°	4469	1939	4454	1872
55°	4117	1598	4084	1587
60°	3772	1321	3735	1349
65°	3365	1057	3387	1143
70°	2992	735	3072	925
75°	2537	546	2640	711
80°	2020	360	2193	533
85°	1441	171	1566	332

MAXIMUM LUMINANCE 45°-90°:

Luminance: 7612 cd/sqm

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.0	1.3
10°-20°	162.8	3.9
20°-30°	256.5	6.2
30°-40°	266.7	6.4
40°-50°	228.2	5.5
50°-60°	173.9	4.2
60°-70°	111.4	2.7
70°-80°	53.4	1.3
80°-90°	16.1	0.4
90°-100°	204.7	4.9
100°-110°	599.2	14.4
110°-120°	585.1	14.1
120°-130°	466.0	11.2
130°-140°	367.6	8.8
140°-150°	274.3	6.6
150°-160°	191.2	4.6
160°-170°	112.3	2.7
170°-180°	36.5	0.9
0°-30°	471.3	11.3
0°-40°	738.0	17.7
0°-60°	1140.1	27.4
0°-90°	1321.1	31.8
90°-120°	1388.9	33.4
90°-150°	2496.8	60.0
90°-180°	2837.0	68.2
0°-180°	4158.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	530	530	530	530	530	
5°	529	629	531	467	529	50
15°	506	894	506	373	506	142
25°	460	921	459	303	460	212
35°	401	400	400	247	401	251
45°	322	213	322	195	322	248
55°	227	134	225	133	227	204
65°	139	77	140	83	139	139
75°	67	33	69	43	67	72
85°	15	8	16	15	15	17
90°	2	22	2	22	2	3
95°	26	89	26	89	26	28
105°	89	971	89	971	89	94
115°	156	1181	156	1181	156	155
125°	218	931	218	931	218	193
135°	255	755	255	755	255	197
145°	291	590	291	590	291	182
155°	331	489	331	489	331	152
165°	361	427	361	427	361	102
175°	376	384	376	384	376	36
180°	377	377	377	377	377	

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	531.1	534.7	537.4	539.2	543.8	546.5	548.8	552.8	552.8	553.7	555.6
5°	529.3	537.0	542.4	549.7	559.2	563.7	570.1	575.5	583.2	587.3	591.4
7.5°	525.2	536.1	547.4	558.3	572.3	581.4	587.8	601.8	611.8	624.0	633.6
10°	519.7	534.7	549.2	566.0	585.0	598.6	608.2	626.8	645.8	663.0	677.6
12.5°	512.9	531.1	551.9	572.3	599.1	612.7	628.1	651.2	678.5	700.2	719.7
15°	505.7	526.5	550.1	575.1	608.6	627.7	649.9	678.0	708.4	739.7	766.4
17.5°	494.3	520.6	546.9	583.2	622.7	634.0	653.1	691.6	729.3	757.4	790.0
20°	483.0	512.5	545.6	578.2	620.9	647.2	664.9	705.7	746.0	780.0	811.3
22.5°	472.6	503.4	537.9	579.1	619.0	645.4	667.6	710.2	756.9	795.0	833.6
25°	459.9	493.4	531.5	570.5	619.0	639.0	663.5	712.9	762.4	806.4	854.0
27.5°	446.3	480.3	517.9	557.8	602.3	631.7	655.8	708.8	769.2	816.3	865.3
30°	432.7	467.6	503.9	539.7	589.6	617.7	645.4	703.9	772.8	826.8	864.4
32.5°	419.5	449.0	484.8	519.7	569.2	600.0	631.3	698.9	774.2	819.5	837.6
35°	401.4	432.2	461.2	498.4	548.3	578.7	615.4	698.4	768.3	796.4	787.3
37.5°	384.6	410.4	438.1	471.2	522.5	561.9	600.0	686.6	748.8	750.6	699.3
40°	366.0	387.3	410.4	445.4	500.7	539.7	581.0	668.5	713.4	686.6	596.4
42.5°	344.7	363.7	381.9	415.9	476.2	519.7	564.2	645.8	662.1	600.5	506.6
45°	322.0	337.4	354.2	390.0	450.3	493.4	537.9	610.9	594.1	507.0	417.7
47.5°	298.4	311.6	327.9	360.5	422.7	466.7	508.8	561.0	518.4	424.9	350.1
50°	274.8	285.3	301.1	334.7	394.6	434.5	473.5	507.5	447.6	364.6	289.3
52.5°	251.7	259.9	276.2	304.8	362.8	400.9	429.0	442.2	381.4	301.1	251.2
55°	227.2	236.3	247.2	276.2	333.8	361.9	380.5	380.0	317.5	255.3	207.7
57.5°	203.6	211.8	221.3	250.3	297.1	316.1	332.0	324.3	264.9	209.1	178.2
60°	182.8	187.3	197.7	222.2	257.6	273.9	283.0	269.8	216.3	176.4	147.4
62.5°	160.1	164.6	173.2	196.4	218.1	226.8	234.5	217.7	178.7	143.8	126.1
65°	139.2	145.1	150.6	169.2	181.0	191.4	190.5	176.4	139.7	117.0	102.5
67.5°	121.1	123.4	127.9	139.2	144.7	152.4	152.8	137.0	112.5	95.2	86.6
70°	101.6	103.9	107.0	112.5	116.1	117.9	117.0	102.9	84.8	74.4	66.7
72.5°	84.8	84.4	86.6	86.6	90.2	89.8	87.1	76.2	64.4	55.8	51.2
75°	66.7	67.1	67.6	66.7	65.3	63.5	61.2	53.1	45.4	41.3	37.2
77.5°	52.2	51.2	51.7	48.5	46.7	44.9	41.7	37.6	31.3	30.4	28.6
80°	37.2	36.7	36.3	34.9	30.8	29.0	26.8	24.5	23.1	22.2	21.8
82.5°	24.9	24.9	24.0	21.3	19.0	17.7	17.2	16.3	15.0	15.0	14.5
85°	15.0	14.5	13.6	10.9	9.5	9.5	9.5	9.5	8.6	8.6	8.2
87.5°	5.9	5.4	4.1	4.1	3.6	3.6	3.6	3.2	3.2	2.7	2.7
90°	1.5	3.1	4.6	6.9	8.4	9.2	9.9	12.2	14.5	16.8	19.1
92.5°	11.5	16.8	24.4	31.3	38.9	45.8	52.7	77.1	117.6	157.3	142.0
95°	26.0	28.2	36.6	49.6	69.5	84.4	99.2	164.1	277.9	403.1	452.7
97.5°	41.2	42.0	48.9	60.3	80.2	96.6	113.0	177.1	309.2	519.9	696.3
100°	56.5	57.3	62.6	73.3	91.6	106.5	121.4	174.8	287.8	488.6	723.0
102.5°	72.5	74.1	78.6	88.6	104.6	118.0	131.3	177.9	269.5	442.8	673.4
105°	88.6	90.9	95.4	104.6	119.1	131.0	142.8	184.0	262.6	406.9	613.8
107.5°	105.4	107.6	112.2	121.4	135.1	146.2	157.3	193.9	261.1	381.0	561.1
110°	123.7	126.0	129.8	138.2	151.2	161.8	172.5	206.9	264.9	367.2	517.6

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	140.5	142.8	146.6	155.0	168.0	178.3	188.6	219.9	272.6	359.6	488.6
115°	156.5	159.6	164.1	171.8	184.8	195.1	205.4	234.4	280.9	358.8	469.5
117.5°	172.5	176.4	180.2	187.0	201.6	211.1	220.6	249.6	291.6	359.6	456.5
120°	189.3	191.6	195.4	203.1	217.6	227.2	236.7	264.2	303.9	362.6	448.1
122.5°	203.8	206.1	209.9	218.3	232.1	242.4	252.7	279.4	315.3	368.0	442.8
125°	217.6	219.1	223.7	232.1	246.6	256.9	267.2	293.9	327.5	373.3	438.2
127.5°	228.3	230.6	235.9	244.3	260.3	270.6	280.9	306.9	337.4	379.4	435.9
130°	238.2	240.5	247.4	256.5	272.6	282.9	293.2	318.4	347.4	385.5	433.6
132.5°	245.8	248.9	256.5	268.0	284.0	294.0	303.9	328.3	356.5	390.1	432.9
135°	255.0	258.0	266.4	277.9	293.9	304.2	314.5	338.2	364.2	394.7	432.1
137.5°	263.4	266.4	274.8	287.1	303.1	312.6	322.2	345.1	370.3	397.8	430.6
140°	271.8	275.6	283.2	295.5	310.7	320.2	329.8	351.9	374.9	400.8	429.8
142.5°	280.9	284.0	292.4	303.1	318.4	327.2	335.9	357.3	379.4	403.1	428.3
145°	290.9	293.2	300.0	311.5	324.5	333.2	342.0	361.9	382.5	403.9	426.8
147.5°	300.8	302.3	309.2	319.1	332.1	339.8	347.4	365.7	384.8	403.9	424.5
150°	310.7	311.5	317.6	327.5	338.2	345.0	351.9	369.5	385.5	403.9	421.4
152.5°	320.6	320.6	326.8	335.2	344.3	350.8	357.3	371.8	387.1	401.6	417.6
155°	330.6	330.6	335.2	342.8	351.2	356.5	361.9	374.9	387.1	400.0	413.0
157.5°	338.2	339.0	342.8	349.7	357.3	361.5	365.7	376.4	387.8	397.8	409.2
160°	347.4	347.4	350.4	356.5	361.9	365.7	369.5	378.7	387.8	396.2	404.6
162.5°	354.2	354.2	356.5	361.1	365.7	368.8	371.8	379.4	387.1	393.2	400.0
165°	361.1	360.3	361.9	365.7	368.7	371.4	374.1	380.2	385.5	390.1	395.5
167.5°	366.5	365.7	366.5	369.5	371.8	373.7	375.6	380.2	384.8	387.1	390.9
170°	371.0	369.5	370.3	372.6	374.1	374.8	375.6	379.4	382.5	384.0	386.3
172.5°	374.1	373.3	373.3	374.9	375.6	376.0	376.4	379.4	381.7	381.7	382.5
175°	376.4	375.6	374.9	376.4	376.4	376.8	377.1	378.7	380.2	379.4	379.4
177.5°	377.9	377.1	376.4	377.1	377.1	377.1	377.1	377.9	379.4	377.9	377.1
180°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	559.2	559.2	563.3	567.3	565.1	566.4	571.4	569.6	573.2	572.8	574.2
5°	601.4	606.4	610.4	619.0	620.4	619.0	627.7	629.9	634.0	629.0	631.3
7.5°	649.0	659.4	669.4	682.1	686.2	687.1	691.6	698.0	703.4	693.4	698.4
10°	695.2	711.1	731.5	742.9	752.8	756.5	760.1	764.2	770.5	776.4	771.9
12.5°	745.1	768.3	787.8	808.2	820.4	819.1	829.5	832.2	837.2	838.6	840.4
15°	785.9	818.6	830.8	861.2	863.9	873.0	884.8	895.2	896.6	893.9	893.9
17.5°	824.9	853.1	874.8	899.3	904.3	912.0	927.0	932.0	933.8	933.3	933.3
20°	856.7	875.3	912.0	932.4	940.6	950.6	961.0	967.4	968.7	970.5	967.8
22.5°	877.6	905.7	935.6	952.4	959.2	962.8	969.6	971.4	969.2	969.6	970.1
25°	893.9	921.5	939.7	944.2	943.8	939.2	934.2	925.6	924.7	921.1	913.8
27.5°	898.4	908.8	906.6	888.0	869.4	867.6	837.6	821.3	802.7	805.4	795.0
30°	873.9	860.3	828.1	781.0	761.5	729.7	696.1	661.2	647.6	632.7	660.3
32.5°	814.1	765.5	708.4	647.2	614.5	586.4	550.6	525.2	510.7	498.4	522.0
35°	723.8	648.1	572.3	514.3	487.5	462.1	428.6	415.9	397.7	399.5	401.8
37.5°	607.7	524.3	467.1	410.0	392.3	381.9	357.4	337.9	331.5	329.7	329.7
40°	498.9	430.4	379.6	334.7	321.1	312.5	293.0	283.9	277.1	275.3	277.6
42.5°	412.7	354.2	314.7	284.8	275.3	264.4	256.2	244.9	243.5	240.4	244.4
45°	346.5	295.7	266.2	244.4	236.3	232.2	223.1	216.3	213.6	213.2	216.3
47.5°	293.9	254.4	228.6	215.0	208.6	204.5	196.8	194.1	191.4	192.3	190.9
50°	246.7	217.2	200.5	188.2	184.1	180.0	175.1	172.3	171.0	171.0	170.5
52.5°	211.8	187.3	176.4	165.1	163.3	161.0	155.6	153.7	151.5	151.0	152.8
55°	181.4	164.6	153.7	146.9	145.1	140.6	138.3	136.1	134.7	133.8	134.2
57.5°	155.1	142.4	135.1	129.3	126.1	124.3	120.2	119.7	118.8	118.8	118.4
60°	133.3	124.3	115.6	112.0	109.8	107.5	107.0	104.3	102.9	103.9	103.4
62.5°	112.9	105.7	100.7	96.6	95.2	93.4	92.1	91.2	89.8	90.2	90.2
65°	94.3	88.4	84.8	81.2	80.7	78.9	78.5	77.6	77.6	77.1	78.0
67.5°	77.6	73.5	70.3	68.0	66.7	67.1	65.3	63.9	63.9	63.5	64.9
70°	61.7	59.4	56.2	53.5	51.7	51.7	49.4	49.0	49.0	49.0	48.5
72.5°	47.6	43.5	42.2	41.3	41.3	41.3	40.4	40.4	39.9	40.4	39.9
75°	35.4	34.9	34.0	33.6	33.6	33.1	32.7	32.7	32.7	32.7	32.7
77.5°	27.7	27.7	26.8	26.3	26.3	26.3	25.9	25.9	25.4	25.4	25.4
80°	20.4	20.4	19.5	19.5	19.5	19.0	19.0	19.0	19.5	19.0	19.0
82.5°	14.1	14.1	13.6	14.1	13.6	13.2	13.2	13.2	12.7	13.2	13.2
85°	8.2	8.2	7.7	7.3	7.7	7.7	7.3	7.7	7.3	7.7	7.3
87.5°	3.2	2.7	2.7	2.7	2.3	2.7	2.3	2.3	2.7	2.3	2.7
90°	18.3	19.1	19.8	20.6	21.4	22.1	21.4	22.1	22.9	22.1	22.9
92.5°	106.1	75.6	58.8	51.2	48.5	45.8	44.3	41.2	42.0	40.5	42.0
95°	367.2	274.8	186.3	145.8	132.0	118.3	103.8	97.0	91.6	88.6	91.6
97.5°	719.9	631.4	476.4	375.6	332.1	288.6	237.4	208.4	190.1	181.7	190.1
100°	873.4	900.1	838.3	748.9	694.7	640.5	563.4	507.7	477.9	478.7	477.9
102.5°	881.0	989.4	1002.4	959.7	930.3	900.9	845.1	803.9	780.2	758.1	780.2
105°	832.9	992.5	1068.8	1083.3	1073.4	1063.5	1028.4	999.4	974.9	971.1	974.9
107.5°	764.2	946.7	1066.5	1126.1	1136.4	1146.7	1142.1	1128.4	1118.5	1110.1	1118.5
110°	700.1	874.9	1015.4	1111.6	1138.3	1165.0	1186.4	1192.5	1191.0	1189.5	1191.0

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	644.4	803.9	948.2	1058.9	1095.2	1131.4	1174.9	1197.1	1204.7	1205.5	1204.7
115°	601.6	742.8	875.7	987.9	1029.5	1071.1	1128.4	1162.0	1177.2	1181.1	1177.2
117.5°	573.3	695.5	813.1	916.1	959.2	1002.4	1062.0	1099.4	1122.3	1127.6	1122.3
120°	552.0	659.6	762.7	854.3	892.8	931.4	991.7	1034.5	1052.8	1057.4	1052.8
122.5°	534.4	631.4	722.2	805.4	840.6	875.7	927.6	965.0	985.6	991.7	985.6
125°	519.9	606.9	690.2	763.4	794.0	824.5	873.4	907.0	926.1	931.4	926.1
127.5°	506.2	584.8	660.4	727.6	755.8	784.1	828.3	857.4	874.9	879.5	874.9
130°	495.5	564.2	632.9	694.7	720.7	746.7	787.1	814.6	830.6	836.7	830.6
132.5°	485.6	545.1	606.9	663.4	687.8	712.3	749.7	777.2	790.9	794.7	790.9
135°	477.2	528.3	582.5	632.1	653.9	675.7	713.1	736.0	749.7	755.1	749.7
137.5°	469.5	512.3	558.1	602.4	621.8	641.3	673.4	697.0	708.5	713.1	708.5
140°	462.6	498.5	537.5	574.1	590.5	606.9	636.0	657.3	669.5	668.8	669.5
142.5°	456.5	485.6	517.6	548.2	561.9	575.6	599.3	617.6	628.3	627.6	628.3
145°	451.2	475.6	500.8	525.3	536.3	547.4	566.5	582.5	588.6	590.1	588.6
147.5°	445.9	467.2	487.8	508.5	516.5	524.5	539.8	551.2	557.3	558.1	557.3
150°	440.5	458.1	475.6	491.7	499.0	506.2	517.6	526.0	530.6	530.6	530.6
152.5°	434.4	449.7	464.2	477.9	483.6	489.4	497.8	505.4	507.7	507.7	507.7
155°	428.3	441.3	453.5	464.9	469.5	474.1	481.0	487.1	488.6	489.4	488.6
157.5°	421.4	432.1	442.8	452.0	455.8	459.6	465.7	470.3	471.8	471.8	471.8
160°	414.6	424.5	432.9	440.5	443.2	445.9	451.2	455.8	455.8	455.0	455.8
162.5°	407.7	415.3	422.2	429.1	431.4	433.6	436.7	440.5	440.5	439.7	440.5
165°	401.6	407.7	412.3	417.6	419.5	421.4	424.5	427.5	426.8	426.8	426.8
167.5°	395.5	400.8	404.6	407.7	409.2	410.7	412.3	414.6	413.8	413.8	413.8
170°	390.1	393.9	396.2	399.3	400.0	400.8	401.6	403.1	402.3	402.3	402.3
172.5°	384.8	387.8	389.4	391.6	392.0	392.4	392.4	393.9	392.4	391.6	392.4
175°	381.0	382.5	383.3	384.8	384.8	384.8	384.8	385.5	384.8	384.0	384.8
177.5°	377.9	378.7	379.4	380.2	380.2	380.2	379.4	380.2	378.7	378.7	378.7
180°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	571.9	569.2	567.3	566.0	564.6	568.7	563.3	557.4	553.3	550.6	549.7
5°	631.7	625.9	620.9	616.8	617.7	617.7	608.2	597.7	588.7	583.7	578.2
7.5°	701.1	694.8	684.8	682.5	680.7	669.4	659.9	640.8	629.5	618.1	608.2
10°	770.1	761.9	752.4	749.2	744.7	730.6	716.1	691.6	677.6	656.7	643.5
12.5°	834.5	824.5	815.0	812.7	805.9	793.7	768.7	743.3	719.3	697.1	673.9
15°	888.4	885.7	871.2	862.1	847.2	830.4	824.9	790.5	760.1	737.0	695.2
17.5°	933.8	921.1	907.5	901.6	895.7	876.2	856.7	821.3	788.7	754.7	727.9
20°	970.1	956.0	946.5	937.9	935.2	912.9	882.1	850.8	815.0	776.9	742.0
22.5°	971.9	970.1	963.7	958.7	953.3	938.8	914.3	875.3	837.2	795.5	749.7
25°	934.2	931.5	949.7	945.1	948.8	943.3	930.2	897.5	853.1	804.1	757.8
27.5°	820.9	848.5	877.1	887.1	893.9	913.4	919.7	901.6	865.8	813.6	761.9
30°	666.7	703.4	749.7	774.6	793.7	829.9	877.1	883.0	866.2	824.5	761.0
32.5°	523.4	556.9	594.1	623.6	649.0	723.4	786.9	832.7	840.8	819.1	763.3
35°	421.8	436.3	471.7	499.8	534.2	597.7	672.6	746.5	796.4	799.1	756.5
37.5°	347.8	355.6	386.4	402.3	422.7	478.5	548.3	644.9	722.5	759.2	737.4
40°	288.0	305.7	323.4	332.4	346.9	385.5	452.6	528.3	624.5	692.5	707.9
42.5°	249.9	257.6	268.9	281.6	290.7	324.3	369.2	438.6	525.2	620.0	662.6
45°	220.4	223.1	234.9	243.1	252.6	276.2	307.9	366.0	442.2	535.6	608.2
47.5°	195.9	201.4	207.7	212.7	219.0	237.2	264.4	306.6	373.7	457.1	535.1
50°	174.2	177.3	185.5	187.8	192.3	205.0	225.9	258.1	313.4	380.0	460.8
52.5°	153.7	159.6	162.8	166.0	170.1	180.5	194.1	220.4	262.1	324.7	393.2
55°	137.9	139.7	144.2	146.9	150.1	157.4	169.2	188.7	221.3	271.2	336.1
57.5°	122.4	122.4	127.0	129.3	132.4	137.9	148.3	163.3	186.8	224.0	283.4
60°	106.1	106.6	110.2	112.9	113.8	119.3	127.9	139.7	157.8	185.0	233.6
62.5°	91.6	93.9	95.7	96.6	99.8	102.9	110.2	118.4	131.1	155.1	189.6
65°	79.4	79.8	81.2	82.1	83.4	87.1	92.5	98.0	108.8	126.5	154.6
67.5°	65.3	67.1	68.9	68.9	70.3	72.1	77.6	82.1	90.2	100.7	119.7
70°	49.0	49.9	52.6	54.0	55.8	59.0	61.7	64.4	70.7	78.5	93.0
72.5°	40.8	40.8	41.7	42.2	42.2	44.4	48.5	51.2	54.4	59.9	69.8
75°	32.7	32.7	34.0	33.6	34.5	35.4	35.8	37.6	39.5	43.5	49.4
77.5°	25.9	26.3	26.3	26.8	26.8	27.2	27.7	28.6	29.5	31.7	34.5
80°	19.0	19.5	19.5	20.0	20.0	20.4	20.9	21.3	22.2	23.1	24.5
82.5°	13.2	13.6	13.6	14.1	13.6	14.1	14.5	14.5	15.0	15.9	16.3
85°	7.7	7.7	8.2	7.7	7.7	7.7	8.2	8.2	8.6	10.0	10.0
87.5°	2.3	2.7	2.3	2.7	2.7	2.7	2.7	3.2	3.2	3.6	4.1
90°	22.1	21.4	22.1	21.4	20.6	19.8	19.1	18.3	19.1	16.8	14.5
92.5°	41.2	44.3	45.8	48.5	51.2	58.8	75.6	106.1	142.0	157.3	117.6
95°	97.0	103.8	118.3	132.0	145.8	186.3	274.8	367.2	452.7	403.1	277.9
97.5°	208.4	237.4	288.6	332.1	375.6	476.4	631.4	719.9	696.3	519.9	309.2
100°	507.7	563.4	640.5	694.7	748.9	838.3	900.1	873.4	723.0	488.6	287.8
102.5°	803.9	845.1	900.9	930.3	959.7	1002.4	989.4	881.0	673.4	442.8	269.5
105°	999.4	1028.4	1063.5	1073.4	1083.3	1068.8	992.5	832.9	613.8	406.9	262.6
107.5°	1128.4	1142.1	1146.7	1136.4	1126.1	1066.5	946.7	764.2	561.1	381.0	261.1
110°	1192.5	1186.4	1165.0	1138.3	1111.6	1015.4	874.9	700.1	517.6	367.2	264.9

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1197.1	1174.9	1131.4	1095.2	1058.9	948.2	803.9	644.4	488.6	359.6	272.6
115°	1162.0	1128.4	1071.1	1029.5	987.9	875.7	742.8	601.6	469.5	358.8	280.9
117.5°	1099.4	1062.0	1002.4	959.2	916.1	813.1	695.5	573.3	456.5	359.6	291.6
120°	1034.5	991.7	931.4	892.8	854.3	762.7	659.6	552.0	448.1	362.6	303.9
122.5°	965.0	927.6	875.7	840.6	805.4	722.2	631.4	534.4	442.8	368.0	315.3
125°	907.0	873.4	824.5	794.0	763.4	690.2	606.9	519.9	438.2	373.3	327.5
127.5°	857.4	828.3	784.1	755.8	727.6	660.4	584.8	506.2	435.9	379.4	337.4
130°	814.6	787.1	746.7	720.7	694.7	632.9	564.2	495.5	433.6	385.5	347.4
132.5°	777.2	749.7	712.3	687.8	663.4	606.9	545.1	485.6	432.9	390.1	356.5
135°	736.0	713.1	675.7	653.9	632.1	582.5	528.3	477.2	432.1	394.7	364.2
137.5°	697.0	673.4	641.3	621.8	602.4	558.1	512.3	469.5	430.6	397.8	370.3
140°	657.3	636.0	606.9	590.5	574.1	537.5	498.5	462.6	429.8	400.8	374.9
142.5°	617.6	599.3	575.6	561.9	548.2	517.6	485.6	456.5	428.3	403.1	379.4
145°	582.5	566.5	547.4	536.3	525.3	500.8	475.6	451.2	426.8	403.9	382.5
147.5°	551.2	539.8	524.5	516.5	508.5	487.8	467.2	445.9	424.5	403.9	384.8
150°	526.0	517.6	506.2	499.0	491.7	475.6	458.1	440.5	421.4	403.9	385.5
152.5°	505.4	497.8	489.4	483.6	477.9	464.2	449.7	434.4	417.6	401.6	387.1
155°	487.1	481.0	474.1	469.5	464.9	453.5	441.3	428.3	413.0	400.0	387.1
157.5°	470.3	465.7	459.6	455.8	452.0	442.8	432.1	421.4	409.2	397.8	387.8
160°	455.8	451.2	445.9	443.2	440.5	432.9	424.5	414.6	404.6	396.2	387.8
162.5°	440.5	436.7	433.6	431.4	429.1	422.2	415.3	407.7	400.0	393.2	387.1
165°	427.5	424.5	421.4	419.5	417.6	412.3	407.7	401.6	395.5	390.1	385.5
167.5°	414.6	412.3	410.7	409.2	407.7	404.6	400.8	395.5	390.9	387.1	384.8
170°	403.1	401.6	400.8	400.0	399.3	396.2	393.9	390.1	386.3	384.0	382.5
172.5°	393.9	392.4	392.4	392.0	391.6	389.4	387.8	384.8	382.5	381.7	381.7
175°	385.5	384.8	384.8	384.8	384.8	383.3	382.5	381.0	379.4	379.4	380.2
177.5°	380.2	379.4	380.2	380.2	380.2	379.4	378.7	377.9	377.1	377.9	379.4
180°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	548.3	546.0	543.8	543.8	538.8	534.2	532.0	532.9	530.2	526.5	522.9
5°	572.3	563.3	561.5	556.5	549.7	540.1	535.1	530.6	525.2	517.9	511.1
7.5°	594.6	582.8	576.4	571.4	558.3	545.1	534.2	527.0	517.5	506.6	498.4
10°	623.6	601.8	595.0	583.7	565.1	546.5	533.8	522.0	508.8	496.1	485.3
12.5°	646.7	621.8	609.1	597.7	573.7	550.1	528.8	514.3	498.4	484.4	470.3
15°	673.0	644.9	622.7	609.1	578.7	550.1	526.1	505.7	488.0	470.7	458.5
17.5°	685.7	650.3	640.4	620.9	576.9	548.3	518.8	497.1	475.7	455.8	441.3
20°	705.7	664.4	639.5	626.3	587.3	545.1	510.7	485.7	463.5	442.2	426.8
22.5°	707.0	662.1	645.8	620.9	572.8	535.6	503.4	473.0	447.2	427.2	411.3
25°	703.9	658.1	635.4	615.4	575.5	530.2	488.9	459.0	433.6	410.4	391.8
27.5°	702.5	646.3	624.9	605.0	560.1	514.3	480.3	446.3	417.2	396.8	377.8
30°	700.7	633.6	607.7	584.6	543.3	502.0	461.2	431.7	404.1	378.2	359.2
32.5°	688.9	616.3	590.0	565.5	521.1	479.8	447.6	416.3	386.4	362.4	345.1
35°	685.3	600.5	566.0	539.7	496.1	459.4	425.4	399.5	371.4	347.4	327.0
37.5°	674.8	584.1	546.9	513.4	468.0	433.1	408.2	382.3	355.1	329.3	312.9
40°	656.7	565.1	522.9	488.4	441.7	406.4	383.2	364.2	337.4	314.3	294.3
42.5°	629.9	545.6	500.2	463.9	412.2	379.1	360.1	342.0	319.3	295.2	278.9
45°	599.1	519.7	477.6	437.2	384.6	352.4	332.4	321.5	300.7	280.3	261.2
47.5°	556.9	493.0	451.2	409.5	356.0	324.7	308.8	298.0	283.4	261.2	245.8
50°	503.9	458.5	419.0	381.9	327.9	298.0	282.1	273.9	261.7	245.8	230.8
52.5°	444.9	418.6	385.9	351.5	299.3	271.2	256.7	250.3	241.3	226.3	213.6
55°	385.5	374.2	351.9	317.9	269.4	246.3	233.6	225.4	218.6	207.7	196.8
57.5°	332.4	327.0	311.6	285.3	244.4	220.4	209.5	204.1	198.6	190.5	179.6
60°	277.6	283.4	267.6	254.4	217.2	196.4	186.8	181.0	178.2	171.0	164.2
62.5°	229.9	235.4	226.3	216.3	190.0	171.4	165.5	160.1	158.3	151.9	145.1
65°	186.8	193.7	186.8	181.4	165.5	150.1	142.9	140.1	138.3	134.2	128.8
67.5°	148.8	155.6	152.4	145.6	140.6	127.9	123.8	121.1	120.2	117.0	112.5
70°	112.0	121.5	122.4	118.4	113.8	107.9	105.2	104.3	102.0	99.3	96.6
72.5°	80.7	91.6	92.1	92.1	89.3	89.3	86.6	85.3	85.3	82.5	79.4
75°	59.4	66.7	67.6	68.5	69.8	71.2	69.4	69.4	68.9	66.2	64.9
77.5°	39.5	45.8	48.1	51.2	53.1	53.1	54.0	54.9	54.0	52.6	51.7
80°	25.4	29.9	32.7	34.5	37.2	38.5	39.9	40.4	39.5	39.0	37.6
82.5°	16.8	18.1	19.5	21.8	24.9	27.2	27.2	26.8	27.7	27.2	26.8
85°	9.5	10.4	10.9	11.3	13.2	15.4	15.9	16.3	17.2	16.3	15.4
87.5°	3.6	4.1	4.1	4.1	5.0	5.4	6.8	8.6	8.2	7.3	7.3
90°	12.2	9.9	9.2	8.4	6.9	4.6	3.1	1.5	3.1	4.6	6.9
92.5°	77.1	52.7	45.8	38.9	31.3	24.4	16.8	11.5	16.8	24.4	31.3
95°	164.1	99.2	84.4	69.5	49.6	36.6	28.2	26.0	28.2	36.6	49.6
97.5°	177.1	113.0	96.6	80.2	60.3	48.9	42.0	41.2	42.0	48.9	60.3
100°	174.8	121.4	106.5	91.6	73.3	62.6	57.3	56.5	57.3	62.6	73.3
102.5°	177.9	131.3	118.0	104.6	88.6	78.6	74.1	72.5	74.1	78.6	88.6
105°	184.0	142.8	131.0	119.1	104.6	95.4	90.9	88.6	90.9	95.4	104.6
107.5°	193.9	157.3	146.2	135.1	121.4	112.2	107.6	105.4	107.6	112.2	121.4
110°	206.9	172.5	161.8	151.2	138.2	129.8	126.0	123.7	126.0	129.8	138.2

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	219.9	188.6	178.3	168.0	155.0	146.6	142.8	140.5	142.8	146.6	155.0
115°	234.4	205.4	195.1	184.8	171.8	164.1	159.6	156.5	159.6	164.1	171.8
117.5°	249.6	220.6	211.1	201.6	187.0	180.2	176.4	172.5	176.4	180.2	187.0
120°	264.2	236.7	227.2	217.6	203.1	195.4	191.6	189.3	191.6	195.4	203.1
122.5°	279.4	252.7	242.4	232.1	218.3	209.9	206.1	203.8	206.1	209.9	218.3
125°	293.9	267.2	256.9	246.6	232.1	223.7	219.1	217.6	219.1	223.7	232.1
127.5°	306.9	280.9	270.6	260.3	244.3	235.9	230.6	228.3	230.6	235.9	244.3
130°	318.4	293.2	282.9	272.6	256.5	247.4	240.5	238.2	240.5	247.4	256.5
132.5°	328.3	303.9	294.0	284.0	268.0	256.5	248.9	245.8	248.9	256.5	268.0
135°	338.2	314.5	304.2	293.9	277.9	266.4	258.0	255.0	258.0	266.4	277.9
137.5°	345.1	322.2	312.6	303.1	287.1	274.8	266.4	263.4	266.4	274.8	287.1
140°	351.9	329.8	320.2	310.7	295.5	283.2	275.6	271.8	275.6	283.2	295.5
142.5°	357.3	335.9	327.2	318.4	303.1	292.4	284.0	280.9	284.0	292.4	303.1
145°	361.9	342.0	333.2	324.5	311.5	300.0	293.2	290.9	293.2	300.0	311.5
147.5°	365.7	347.4	339.8	332.1	319.1	309.2	302.3	300.8	302.3	309.2	319.1
150°	369.5	351.9	345.0	338.2	327.5	317.6	311.5	310.7	311.5	317.6	327.5
152.5°	371.8	357.3	350.8	344.3	335.2	326.8	320.6	320.6	320.6	326.8	335.2
155°	374.9	361.9	356.5	351.2	342.8	335.2	330.6	330.6	330.6	335.2	342.8
157.5°	376.4	365.7	361.5	357.3	349.7	342.8	339.0	338.2	339.0	342.8	349.7
160°	378.7	369.5	365.7	361.9	356.5	350.4	347.4	347.4	347.4	350.4	356.5
162.5°	379.4	371.8	368.8	365.7	361.1	356.5	354.2	354.2	354.2	356.5	361.1
165°	380.2	374.1	371.4	368.7	365.7	361.9	360.3	361.1	360.3	361.9	365.7
167.5°	380.2	375.6	373.7	371.8	369.5	366.5	365.7	366.5	365.7	366.5	369.5
170°	379.4	375.6	374.8	374.1	372.6	370.3	369.5	371.0	369.5	370.3	372.6
172.5°	379.4	376.4	376.0	375.6	374.9	373.3	373.3	374.1	373.3	373.3	374.9
175°	378.7	377.1	376.8	376.4	376.4	374.9	375.6	376.4	375.6	374.9	376.4
177.5°	377.9	377.1	377.1	377.1	377.1	376.4	377.1	377.9	377.1	376.4	377.1
180°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	522.9	520.6	519.7	517.5	512.0	508.4	504.3	501.6	502.0	499.8	501.1
5°	506.6	506.1	502.9	498.4	490.7	486.6	479.4	475.7	473.9	474.4	471.7
7.5°	493.0	488.9	486.6	479.4	472.1	463.5	457.6	454.4	451.7	449.0	447.2
10°	477.6	473.9	470.3	462.6	452.6	444.4	436.3	433.1	429.0	427.2	425.9
12.5°	461.2	459.0	454.4	445.4	434.0	426.3	416.8	415.0	409.5	405.9	405.0
15°	446.3	444.9	436.7	426.3	415.0	407.3	399.1	393.7	384.6	386.4	383.2
17.5°	430.4	424.5	419.5	405.4	400.0	388.2	378.7	376.0	369.6	365.5	361.5
20°	412.7	409.1	402.7	393.7	380.5	366.9	359.6	355.1	351.5	345.1	343.3
22.5°	395.9	391.4	385.9	374.2	362.8	351.5	341.5	337.4	332.9	328.3	325.6
25°	382.8	376.0	370.1	355.6	344.2	334.7	328.3	321.5	315.2	312.5	311.6
27.5°	362.4	358.3	352.4	338.8	328.3	317.9	312.0	307.5	300.7	297.5	294.8
30°	349.2	341.0	334.2	323.4	312.9	301.6	296.1	290.7	286.6	282.5	279.4
32.5°	331.5	325.2	319.7	308.8	298.4	288.0	282.1	273.9	271.7	268.5	264.9
35°	314.3	310.2	304.3	292.5	281.2	273.9	267.6	259.9	257.1	254.9	251.7
37.5°	298.0	292.1	288.0	276.6	266.7	258.1	253.1	246.7	244.9	242.2	239.9
40°	283.9	278.0	273.9	262.6	252.2	243.1	239.9	233.6	230.8	227.7	226.3
42.5°	268.0	263.0	257.6	249.4	238.5	229.5	223.1	219.5	215.9	214.5	211.8
45°	251.2	246.7	242.6	233.6	222.2	215.9	210.4	205.4	202.7	200.5	198.6
47.5°	236.7	232.7	227.2	217.2	208.2	202.3	196.8	191.8	189.1	186.4	184.1
50°	220.0	217.7	211.8	202.3	193.7	186.8	181.9	177.3	175.5	172.3	168.7
52.5°	205.0	200.9	195.9	188.2	180.5	172.3	165.5	162.8	159.6	157.8	154.6
55°	187.3	184.6	179.1	172.3	164.2	157.4	152.4	148.8	144.7	142.9	138.8
57.5°	172.3	167.3	164.6	156.0	148.3	141.5	137.9	134.2	129.7	127.0	125.2
60°	156.0	151.5	147.4	140.1	134.7	127.4	122.0	118.8	115.6	112.0	110.2
62.5°	140.1	136.5	131.5	125.6	118.8	112.9	108.8	104.3	102.5	98.9	97.5
65°	122.9	120.2	116.1	109.3	103.9	98.9	94.8	91.2	89.3	88.0	87.1
67.5°	107.5	103.9	101.1	95.2	89.3	85.3	83.0	80.7	78.5	77.1	75.7
70°	91.6	88.9	86.2	80.7	76.6	73.0	71.2	69.4	68.0	66.7	65.3
72.5°	75.3	73.9	71.2	67.6	64.4	61.7	60.3	58.1	56.7	54.4	53.5
75°	62.1	59.9	58.5	55.3	52.6	50.3	48.5	45.8	44.0	43.1	42.6
77.5°	49.0	48.1	46.3	43.5	42.2	39.9	37.2	36.3	35.4	35.4	34.9
80°	36.7	35.4	34.0	31.7	30.4	28.6	28.6	28.6	28.1	28.6	28.1
82.5°	24.9	24.0	23.1	21.8	21.3	21.3	21.8	21.8	21.8	21.8	21.8
85°	14.5	14.5	14.5	15.0	14.5	14.5	15.0	15.4	15.0	15.0	14.5
87.5°	6.8	6.8	7.3	7.3	7.7	7.7	7.7	7.7	7.7	7.7	8.2
90°	8.4	9.2	9.9	12.2	14.5	16.8	19.1	18.3	19.1	19.8	20.6
92.5°	38.9	45.8	52.7	77.1	117.6	157.3	142.0	106.1	75.6	58.8	51.2
95°	69.5	84.4	99.2	164.1	277.9	403.1	452.7	367.2	274.8	186.3	145.8
97.5°	80.2	96.6	113.0	177.1	309.2	519.9	696.3	719.9	631.4	476.4	375.6
100°	91.6	106.5	121.4	174.8	287.8	488.6	723.0	873.4	900.1	838.3	748.9
102.5°	104.6	118.0	131.3	177.9	269.5	442.8	673.4	881.0	989.4	1002.4	959.7
105°	119.1	131.0	142.8	184.0	262.6	406.9	613.8	832.9	992.5	1068.8	1083.3
107.5°	135.1	146.2	157.3	193.9	261.1	381.0	561.1	764.2	946.7	1066.5	1126.1
110°	151.2	161.8	172.5	206.9	264.9	367.2	517.6	700.1	874.9	1015.4	1111.6

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	168.0	178.3	188.6	219.9	272.6	359.6	488.6	644.4	803.9	948.2	1058.9
115°	184.8	195.1	205.4	234.4	280.9	358.8	469.5	601.6	742.8	875.7	987.9
117.5°	201.6	211.1	220.6	249.6	291.6	359.6	456.5	573.3	695.5	813.1	916.1
120°	217.6	227.2	236.7	264.2	303.9	362.6	448.1	552.0	659.6	762.7	854.3
122.5°	232.1	242.4	252.7	279.4	315.3	368.0	442.8	534.4	631.4	722.2	805.4
125°	246.6	256.9	267.2	293.9	327.5	373.3	438.2	519.9	606.9	690.2	763.4
127.5°	260.3	270.6	280.9	306.9	337.4	379.4	435.9	506.2	584.8	660.4	727.6
130°	272.6	282.9	293.2	318.4	347.4	385.5	433.6	495.5	564.2	632.9	694.7
132.5°	284.0	294.0	303.9	328.3	356.5	390.1	432.9	485.6	545.1	606.9	663.4
135°	293.9	304.2	314.5	338.2	364.2	394.7	432.1	477.2	528.3	582.5	632.1
137.5°	303.1	312.6	322.2	345.1	370.3	397.8	430.6	469.5	512.3	558.1	602.4
140°	310.7	320.2	329.8	351.9	374.9	400.8	429.8	462.6	498.5	537.5	574.1
142.5°	318.4	327.2	335.9	357.3	379.4	403.1	428.3	456.5	485.6	517.6	548.2
145°	324.5	333.2	342.0	361.9	382.5	403.9	426.8	451.2	475.6	500.8	525.3
147.5°	332.1	339.8	347.4	365.7	384.8	403.9	424.5	445.9	467.2	487.8	508.5
150°	338.2	345.0	351.9	369.5	385.5	403.9	421.4	440.5	458.1	475.6	491.7
152.5°	344.3	350.8	357.3	371.8	387.1	401.6	417.6	434.4	449.7	464.2	477.9
155°	351.2	356.5	361.9	374.9	387.1	400.0	413.0	428.3	441.3	453.5	464.9
157.5°	357.3	361.5	365.7	376.4	387.8	397.8	409.2	421.4	432.1	442.8	452.0
160°	361.9	365.7	369.5	378.7	387.8	396.2	404.6	414.6	424.5	432.9	440.5
162.5°	365.7	368.8	371.8	379.4	387.1	393.2	400.0	407.7	415.3	422.2	429.1
165°	368.7	371.4	374.1	380.2	385.5	390.1	395.5	401.6	407.7	412.3	417.6
167.5°	371.8	373.7	375.6	380.2	384.8	387.1	390.9	395.5	400.8	404.6	407.7
170°	374.1	374.8	375.6	379.4	382.5	384.0	386.3	390.1	393.9	396.2	399.3
172.5°	375.6	376.0	376.4	379.4	381.7	381.7	382.5	384.8	387.8	389.4	391.6
175°	376.4	376.8	377.1	378.7	380.2	379.4	379.4	381.0	382.5	383.3	384.8
177.5°	377.1	377.1	377.1	377.9	379.4	377.9	377.1	377.9	378.7	379.4	380.2
180°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	500.7	501.1	499.8	497.1	496.6	497.5	500.2	499.3	497.1	501.1	497.5
5°	473.0	470.7	469.8	470.7	468.0	466.7	469.4	468.0	469.4	469.8	471.2
7.5°	446.3	446.7	444.0	444.4	440.8	441.7	441.7	441.7	443.1	444.0	445.8
10°	423.1	424.0	420.9	421.3	418.6	416.8	418.1	420.9	420.9	420.9	421.8
12.5°	404.5	400.5	398.2	397.7	394.6	393.7	396.4	397.3	399.5	399.5	400.9
15°	381.4	380.5	378.7	378.7	371.0	372.8	373.7	376.9	381.4	377.8	378.7
17.5°	360.5	358.3	356.0	355.1	354.2	351.5	355.1	354.6	357.4	357.8	359.2
20°	342.0	340.1	335.6	336.1	337.0	332.9	335.1	335.1	337.9	340.6	343.8
22.5°	323.8	322.0	319.7	320.6	317.9	317.0	317.0	319.3	322.5	324.7	324.3
25°	309.8	306.6	305.2	303.9	302.5	303.4	302.0	304.3	306.6	307.9	306.6
27.5°	293.9	292.5	289.8	288.4	286.2	287.1	288.0	289.8	291.2	291.2	292.5
30°	278.5	276.6	275.7	274.4	274.4	272.6	273.0	274.8	276.2	277.6	279.4
32.5°	263.5	262.1	260.8	260.8	259.9	259.4	259.0	261.7	261.7	264.4	264.4
35°	251.2	249.0	249.0	246.7	247.6	247.2	246.3	248.1	248.5	250.3	249.9
37.5°	237.6	237.6	236.7	234.5	232.7	233.1	235.4	235.4	236.7	236.3	237.6
40°	224.0	223.1	223.1	221.8	221.3	220.9	221.3	221.8	224.0	223.6	224.0
42.5°	210.4	210.9	208.6	208.6	208.6	207.3	207.7	208.2	209.1	210.0	211.3
45°	197.3	196.4	195.9	195.0	194.1	194.6	194.1	195.9	195.5	196.4	197.7
47.5°	183.2	181.9	181.4	179.6	179.6	180.5	180.0	181.4	181.9	183.2	182.3
50°	169.6	167.8	166.4	166.9	164.2	165.1	165.1	166.4	167.8	168.3	169.2
52.5°	153.7	153.3	152.8	150.6	150.1	149.7	150.1	150.6	152.4	153.7	154.2
55°	138.3	137.9	135.1	134.2	132.9	132.9	133.8	134.2	137.4	137.9	139.7
57.5°	124.3	122.9	119.7	119.3	119.3	119.3	117.9	119.7	120.6	122.9	122.9
60°	108.8	108.8	106.1	106.1	106.6	106.1	106.1	106.6	106.6	108.4	109.3
62.5°	96.6	96.1	96.1	95.2	94.8	95.2	94.8	94.8	95.2	96.6	98.0
65°	85.7	85.3	84.8	84.4	83.4	83.4	83.9	84.8	84.8	85.7	86.2
67.5°	75.3	75.3	74.4	74.4	73.9	73.5	73.9	73.5	75.3	75.3	75.7
70°	64.9	64.4	63.0	62.6	61.2	61.7	61.7	63.0	63.5	64.4	65.3
72.5°	52.2	52.2	51.2	50.3	50.8	49.9	49.9	50.3	50.3	51.7	52.2
75°	43.1	42.2	41.7	42.2	41.7	42.6	41.7	41.7	42.6	42.6	42.6
77.5°	35.4	35.4	34.9	34.9	35.4	34.9	35.4	35.4	35.4	34.9	35.4
80°	29.0	28.6	28.6	28.6	28.1	28.1	28.1	28.1	28.1	28.1	28.1
82.5°	21.8	21.8	21.3	21.8	21.8	21.3	21.8	21.3	21.3	21.8	21.8
85°	14.5	15.4	14.5	14.5	15.0	15.0	15.4	15.0	15.4	14.5	15.0
87.5°	7.7	8.2	8.2	7.7	7.7	8.2	8.2	8.2	8.6	7.7	8.2
90°	21.4	22.1	21.4	22.1	22.9	22.1	22.9	22.1	21.4	22.1	21.4
92.5°	48.5	45.8	44.3	41.2	42.0	40.5	42.0	41.2	44.3	45.8	48.5
95°	132.0	118.3	103.8	97.0	91.6	88.6	91.6	97.0	103.8	118.3	132.0
97.5°	332.1	288.6	237.4	208.4	190.1	181.7	190.1	208.4	237.4	288.6	332.1
100°	694.7	640.5	563.4	507.7	477.9	478.7	477.9	507.7	563.4	640.5	694.7
102.5°	930.3	900.9	845.1	803.9	780.2	758.1	780.2	803.9	845.1	900.9	930.3
105°	1073.4	1063.5	1028.4	999.4	974.9	971.1	974.9	999.4	1028.4	1063.5	1073.4
107.5°	1136.4	1146.7	1142.1	1128.4	1118.5	1110.1	1118.5	1128.4	1142.1	1146.7	1136.4
110°	1138.3	1165.0	1186.4	1192.5	1191.0	1189.5	1191.0	1192.5	1186.4	1165.0	1138.3

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1095.2	1131.4	1174.9	1197.1	1204.7	1205.5	1204.7	1197.1	1174.9	1131.4	1095.2
115°	1029.5	1071.1	1128.4	1162.0	1177.2	1181.1	1177.2	1162.0	1128.4	1071.1	1029.5
117.5°	959.2	1002.4	1062.0	1099.4	1122.3	1127.6	1122.3	1099.4	1062.0	1002.4	959.2
120°	892.8	931.4	991.7	1034.5	1052.8	1057.4	1052.8	1034.5	991.7	931.4	892.8
122.5°	840.6	875.7	927.6	965.0	985.6	991.7	985.6	965.0	927.6	875.7	840.6
125°	794.0	824.5	873.4	907.0	926.1	931.4	926.1	907.0	873.4	824.5	794.0
127.5°	755.8	784.1	828.3	857.4	874.9	879.5	874.9	857.4	828.3	784.1	755.8
130°	720.7	746.7	787.1	814.6	830.6	836.7	830.6	814.6	787.1	746.7	720.7
132.5°	687.8	712.3	749.7	777.2	790.9	794.7	790.9	777.2	749.7	712.3	687.8
135°	653.9	675.7	713.1	736.0	749.7	755.1	749.7	736.0	713.1	675.7	653.9
137.5°	621.8	641.3	673.4	697.0	708.5	713.1	708.5	697.0	673.4	641.3	621.8
140°	590.5	606.9	636.0	657.3	669.5	668.8	669.5	657.3	636.0	606.9	590.5
142.5°	561.9	575.6	599.3	617.6	628.3	627.6	628.3	617.6	599.3	575.6	561.9
145°	536.3	547.4	566.5	582.5	588.6	590.1	588.6	582.5	566.5	547.4	536.3
147.5°	516.5	524.5	539.8	551.2	557.3	558.1	557.3	551.2	539.8	524.5	516.5
150°	499.0	506.2	517.6	526.0	530.6	530.6	530.6	526.0	517.6	506.2	499.0
152.5°	483.6	489.4	497.8	505.4	507.7	507.7	507.7	505.4	497.8	489.4	483.6
155°	469.5	474.1	481.0	487.1	488.6	489.4	488.6	487.1	481.0	474.1	469.5
157.5°	455.8	459.6	465.7	470.3	471.8	471.8	471.8	470.3	465.7	459.6	455.8
160°	443.2	445.9	451.2	455.8	455.8	455.0	455.8	455.8	451.2	445.9	443.2
162.5°	431.4	433.6	436.7	440.5	440.5	439.7	440.5	440.5	436.7	433.6	431.4
165°	419.5	421.4	424.5	427.5	426.8	426.8	426.8	427.5	424.5	421.4	419.5
167.5°	409.2	410.7	412.3	414.6	413.8	413.8	413.8	414.6	412.3	410.7	409.2
170°	400.0	400.8	401.6	403.1	402.3	402.3	402.3	403.1	401.6	400.8	400.0
172.5°	392.0	392.4	392.4	393.9	392.4	391.6	392.4	393.9	392.4	392.4	392.0
175°	384.8	384.8	384.8	385.5	384.8	384.0	384.8	385.5	384.8	384.8	384.8
177.5°	380.2	380.2	379.4	380.2	378.7	378.7	378.7	380.2	379.4	380.2	380.2
180°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	501.1	502.9	501.1	497.5	501.1	503.4	505.7	509.3	511.1	511.1	513.8
5°	472.6	476.2	474.8	473.9	477.6	479.8	483.4	488.0	493.0	496.1	499.8
7.5°	447.2	449.4	451.7	451.7	455.3	460.3	465.8	471.2	477.6	482.1	484.8
10°	424.9	426.8	428.1	429.9	435.4	440.8	448.1	454.9	460.3	465.3	469.8
12.5°	403.6	406.4	409.5	410.9	415.0	421.8	428.6	436.7	445.4	450.3	454.9
15°	383.2	384.6	388.2	392.3	395.9	403.2	411.8	420.4	427.7	435.4	439.5
17.5°	362.4	362.8	372.3	370.1	381.9	388.7	393.2	401.4	413.2	419.5	425.9
20°	342.0	346.5	350.6	352.8	359.2	366.9	380.0	386.4	395.9	401.8	407.3
22.5°	326.1	332.9	332.9	338.3	341.5	348.8	358.3	370.5	381.0	385.0	392.7
25°	312.0	315.2	320.6	322.5	328.3	334.7	341.0	354.2	365.5	371.0	376.4
27.5°	293.9	298.0	305.2	305.2	312.9	319.7	327.4	336.1	347.4	355.1	361.0
30°	279.8	283.9	287.1	292.1	295.2	301.6	315.2	321.5	331.5	338.3	345.6
32.5°	266.7	269.8	272.6	278.0	281.6	288.9	296.1	307.5	316.1	322.5	330.2
35°	252.2	255.3	259.0	263.0	268.5	275.3	282.1	291.6	300.2	306.1	312.5
37.5°	238.5	240.8	246.3	249.0	253.5	259.9	268.5	278.5	286.2	290.7	297.1
40°	225.4	227.2	231.3	236.3	239.5	244.4	253.5	262.1	271.7	277.1	282.1
42.5°	211.3	213.6	217.2	222.2	227.2	232.7	237.6	247.6	256.2	260.8	266.2
45°	199.1	200.5	203.2	208.2	213.2	217.2	224.9	234.0	242.2	245.8	251.7
47.5°	184.6	185.9	190.0	192.3	197.7	203.2	210.9	220.0	227.2	230.8	236.3
50°	169.6	171.0	173.7	178.7	182.3	188.2	195.0	202.7	211.8	216.8	220.0
52.5°	155.1	157.8	160.1	164.2	168.7	174.6	181.0	188.2	195.9	200.9	204.5
55°	140.6	142.9	145.6	147.8	153.3	158.7	166.0	172.8	179.6	184.1	188.2
57.5°	124.3	127.4	130.2	134.7	138.8	143.3	151.5	156.9	165.1	168.3	171.9
60°	110.2	113.4	115.6	119.3	122.9	128.8	134.2	141.0	147.8	151.9	156.5
62.5°	98.4	99.8	101.1	104.8	108.4	113.8	119.3	126.1	133.3	135.6	139.2
65°	86.6	88.0	90.2	93.4	96.1	99.3	105.2	110.7	117.5	121.1	122.4
67.5°	76.6	78.0	78.5	80.7	83.0	86.6	89.8	95.2	101.6	103.9	106.6
70°	65.3	67.6	68.0	69.8	70.7	73.0	76.6	80.7	85.7	89.8	92.1
72.5°	52.2	55.3	56.2	59.0	60.3	62.6	65.3	68.5	71.7	73.5	75.3
75°	42.6	43.5	44.0	46.3	48.5	51.7	53.1	54.9	57.6	59.9	61.7
77.5°	35.4	35.8	36.3	36.3	36.7	38.5	41.3	43.5	45.4	46.3	47.6
80°	28.6	28.1	28.1	28.6	28.6	28.6	29.5	32.7	33.6	35.8	35.4
82.5°	22.2	21.3	21.8	21.3	21.3	21.3	21.3	21.8	21.8	23.1	24.0
85°	14.5	15.0	14.5	14.5	14.1	14.5	14.1	14.1	13.6	13.6	13.2
87.5°	7.7	8.2	7.7	7.7	7.3	7.7	7.3	7.3	6.8	6.8	5.9
90°	20.6	19.8	19.1	18.3	19.1	16.8	14.5	12.2	9.9	9.2	8.4
92.5°	51.2	58.8	75.6	106.1	142.0	157.3	117.6	77.1	52.7	45.8	38.9
95°	145.8	186.3	274.8	367.2	452.7	403.1	277.9	164.1	99.2	84.4	69.5
97.5°	375.6	476.4	631.4	719.9	696.3	519.9	309.2	177.1	113.0	96.6	80.2
100°	748.9	838.3	900.1	873.4	723.0	488.6	287.8	174.8	121.4	106.5	91.6
102.5°	959.7	1002.4	989.4	881.0	673.4	442.8	269.5	177.9	131.3	118.0	104.6
105°	1083.3	1068.8	992.5	832.9	613.8	406.9	262.6	184.0	142.8	131.0	119.1
107.5°	1126.1	1066.5	946.7	764.2	561.1	381.0	261.1	193.9	157.3	146.2	135.1
110°	1111.6	1015.4	874.9	700.1	517.6	367.2	264.9	206.9	172.5	161.8	151.2

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1058.9	948.2	803.9	644.4	488.6	359.6	272.6	219.9	188.6	178.3	168.0
115°	987.9	875.7	742.8	601.6	469.5	358.8	280.9	234.4	205.4	195.1	184.8
117.5°	916.1	813.1	695.5	573.3	456.5	359.6	291.6	249.6	220.6	211.1	201.6
120°	854.3	762.7	659.6	552.0	448.1	362.6	303.9	264.2	236.7	227.2	217.6
122.5°	805.4	722.2	631.4	534.4	442.8	368.0	315.3	279.4	252.7	242.4	232.1
125°	763.4	690.2	606.9	519.9	438.2	373.3	327.5	293.9	267.2	256.9	246.6
127.5°	727.6	660.4	584.8	506.2	435.9	379.4	337.4	306.9	280.9	270.6	260.3
130°	694.7	632.9	564.2	495.5	433.6	385.5	347.4	318.4	293.2	282.9	272.6
132.5°	663.4	606.9	545.1	485.6	432.9	390.1	356.5	328.3	303.9	294.0	284.0
135°	632.1	582.5	528.3	477.2	432.1	394.7	364.2	338.2	314.5	304.2	293.9
137.5°	602.4	558.1	512.3	469.5	430.6	397.8	370.3	345.1	322.2	312.6	303.1
140°	574.1	537.5	498.5	462.6	429.8	400.8	374.9	351.9	329.8	320.2	310.7
142.5°	548.2	517.6	485.6	456.5	428.3	403.1	379.4	357.3	335.9	327.2	318.4
145°	525.3	500.8	475.6	451.2	426.8	403.9	382.5	361.9	342.0	333.2	324.5
147.5°	508.5	487.8	467.2	445.9	424.5	403.9	384.8	365.7	347.4	339.8	332.1
150°	491.7	475.6	458.1	440.5	421.4	403.9	385.5	369.5	351.9	345.0	338.2
152.5°	477.9	464.2	449.7	434.4	417.6	401.6	387.1	371.8	357.3	350.8	344.3
155°	464.9	453.5	441.3	428.3	413.0	400.0	387.1	374.9	361.9	356.5	351.2
157.5°	452.0	442.8	432.1	421.4	409.2	397.8	387.8	376.4	365.7	361.5	357.3
160°	440.5	432.9	424.5	414.6	404.6	396.2	387.8	378.7	369.5	365.7	361.9
162.5°	429.1	422.2	415.3	407.7	400.0	393.2	387.1	379.4	371.8	368.8	365.7
165°	417.6	412.3	407.7	401.6	395.5	390.1	385.5	380.2	374.1	371.4	368.7
167.5°	407.7	404.6	400.8	395.5	390.9	387.1	384.8	380.2	375.6	373.7	371.8
170°	399.3	396.2	393.9	390.1	386.3	384.0	382.5	379.4	375.6	374.8	374.1
172.5°	391.6	389.4	387.8	384.8	382.5	381.7	381.7	379.4	376.4	376.0	375.6
175°	384.8	383.3	382.5	381.0	379.4	379.4	380.2	378.7	377.1	376.8	376.4
177.5°	380.2	379.4	378.7	377.9	377.1	377.9	379.4	377.9	377.1	377.1	377.1
180°	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1	377.1

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	529.7	529.7	529.7	529.7
2.5°	516.1	519.3	525.6	531.1
5°	505.2	510.2	519.7	529.3
7.5°	492.1	499.8	512.0	525.2
10°	479.4	489.3	504.3	519.7
12.5°	466.7	477.1	493.0	512.9
15°	451.7	462.6	481.6	505.7
17.5°	438.6	453.1	470.3	494.3
20°	424.5	435.4	457.6	483.0
22.5°	406.8	424.9	445.8	472.6
25°	392.7	408.6	429.5	459.9
27.5°	375.5	394.1	419.5	446.3
30°	361.5	376.9	400.5	432.7
32.5°	345.1	363.3	387.8	419.5
35°	330.6	346.0	369.2	401.4
37.5°	313.4	330.2	356.0	384.6
40°	298.4	314.7	339.2	366.0
42.5°	280.3	297.5	322.0	344.7
45°	265.8	281.6	301.1	322.0
47.5°	248.1	264.9	283.9	298.4
50°	232.2	247.6	262.6	274.8
52.5°	215.0	229.0	242.6	251.7
55°	199.1	210.0	220.9	227.2
57.5°	180.5	190.9	200.0	203.6
60°	164.2	172.8	178.7	182.8
62.5°	146.9	153.3	157.8	160.1
65°	130.2	134.7	137.0	139.2
67.5°	112.9	117.0	118.4	121.1
70°	94.8	99.3	100.2	101.6
72.5°	81.2	81.2	83.0	84.8
75°	64.9	65.8	66.7	66.7
77.5°	50.8	50.8	51.7	52.2
80°	37.2	37.6	37.6	37.2
82.5°	25.4	26.3	25.4	24.9
85°	14.1	15.9	15.0	15.0
87.5°	5.9	5.9	6.8	5.9
90°	6.9	4.6	3.1	1.5
92.5°	31.3	24.4	16.8	11.5
95°	49.6	36.6	28.2	26.0
97.5°	60.3	48.9	42.0	41.2
100°	73.3	62.6	57.3	56.5
102.5°	88.6	78.6	74.1	72.5
105°	104.6	95.4	90.9	88.6
107.5°	121.4	112.2	107.6	105.4
110°	138.2	129.8	126.0	123.7

TEST NUMBER: P1012532

CATALOG NUMBER: S123RDIP-B340D805UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	155.0	146.6	142.8	140.5
115°	171.8	164.1	159.6	156.5
117.5°	187.0	180.2	176.4	172.5
120°	203.1	195.4	191.6	189.3
122.5°	218.3	209.9	206.1	203.8
125°	232.1	223.7	219.1	217.6
127.5°	244.3	235.9	230.6	228.3
130°	256.5	247.4	240.5	238.2
132.5°	268.0	256.5	248.9	245.8
135°	277.9	266.4	258.0	255.0
137.5°	287.1	274.8	266.4	263.4
140°	295.5	283.2	275.6	271.8
142.5°	303.1	292.4	284.0	280.9
145°	311.5	300.0	293.2	290.9
147.5°	319.1	309.2	302.3	300.8
150°	327.5	317.6	311.5	310.7
152.5°	335.2	326.8	320.6	320.6
155°	342.8	335.2	330.6	330.6
157.5°	349.7	342.8	339.0	338.2
160°	356.5	350.4	347.4	347.4
162.5°	361.1	356.5	354.2	354.2
165°	365.7	361.9	360.3	361.1
167.5°	369.5	366.5	365.7	366.5
170°	372.6	370.3	369.5	371.0
172.5°	374.9	373.3	373.3	374.1
175°	376.4	374.9	375.6	376.4
177.5°	377.1	376.4	377.1	377.9
180°	377.1	377.1	377.1	377.1

(END OF REPORT)