

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012537

Luminaire Tested: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012537
REPORT IS A COMBINATION OF REPORTS P993303 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D805UB35-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4177.0 lumens
Efficiency: N/A
Efficacy: 122.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	30	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	28	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	25	24	22
5	66	55	47	42	59	50	43	38	40	36	32	31	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	28	25	22	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	22	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14
9	49	37	30	25	44	34	27	23	28	23	20	22	18	16	16	14	12
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5727	5727	5727	5727
5°	5732	6597	5747	4894
10°	5681	7964	5707	4275
15°	5623	9037	5623	3769
20°	5508	9748	5538	3344
25°	5424	9262	5412	3051
30°	5325	6417	5314	2765
35°	5207	4120	5184	2549
40°	5061	2909	5034	2334
45°	4804	2328	4797	2125
50°	4490	1948	4475	1880
55°	4135	1605	4102	1594
60°	3788	1326	3751	1356
65°	3382	1061	3404	1149
70°	3004	738	3086	930
75°	2549	547	2651	714
80°	2030	362	2199	535
85°	1441	171	1575	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7647 cd/sqm

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	1.3
10°-20°	163.6	3.9
20°-30°	257.6	6.2
30°-40°	267.9	6.4
40°-50°	229.2	5.5
50°-60°	174.7	4.2
60°-70°	111.9	2.7
70°-80°	53.6	1.3
80°-90°	16.2	0.4
90°-100°	205.6	4.9
100°-110°	601.9	14.4
110°-120°	587.8	14.1
120°-130°	468.1	11.2
130°-140°	369.3	8.8
140°-150°	275.5	6.6
150°-160°	192.1	4.6
160°-170°	112.8	2.7
170°-180°	36.7	0.9
0°-30°	473.5	11.3
0°-40°	741.4	17.7
0°-60°	1145.3	27.4
0°-90°	1327.1	31.8
90°-120°	1395.3	33.4
90°-150°	2508.2	60.0
90°-180°	2850.0	68.2
0°-180°	4177.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	532	532	532	532	532	
5°	532	632	533	469	532	50
15°	508	898	508	374	508	143
25°	462	925	461	305	462	213
35°	403	401	401	248	403	252
45°	324	214	323	195	324	249
55°	228	134	226	134	228	205
65°	140	77	141	84	140	140
75°	67	33	70	43	67	72
85°	15	8	16	15	15	17
90°	2	22	2	22	2	3
95°	26	89	26	89	26	28
105°	89	976	89	976	89	94
115°	157	1186	157	1186	157	156
125°	219	936	219	936	219	194
135°	256	758	256	758	256	198
145°	292	593	292	593	292	183
155°	332	492	332	492	332	153
165°	363	429	363	429	363	102
175°	378	386	378	386	378	36
180°	379	379	379	379	379	

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	533.5	537.1	539.9	541.7	546.2	549.0	551.3	555.4	555.4	556.3	558.1
5°	531.7	539.4	544.9	552.2	561.7	566.3	572.7	578.1	585.9	590.0	594.1
7.5°	527.6	538.5	549.9	560.8	574.9	584.1	590.4	604.6	614.6	626.9	636.4
10°	522.1	537.1	551.7	568.6	587.7	601.4	610.9	629.6	648.7	666.1	680.6
12.5°	515.3	533.5	554.4	574.9	601.8	615.5	631.0	654.2	681.5	703.4	723.0
15°	508.0	528.9	552.6	577.7	611.4	630.5	652.8	681.1	711.6	743.0	769.9
17.5°	496.6	523.0	549.4	585.9	625.5	636.9	656.0	694.8	732.6	760.8	793.6
20°	485.2	514.8	548.1	580.9	623.7	650.1	667.9	708.9	749.4	783.6	815.0
22.5°	474.7	505.7	540.3	581.8	621.9	648.3	670.6	713.4	760.4	798.6	837.4
25°	462.0	495.7	533.9	573.1	621.9	641.9	666.5	716.2	765.8	810.0	857.9
27.5°	448.3	482.5	520.3	560.4	605.0	634.6	658.8	712.1	772.7	820.0	869.2
30°	434.6	469.7	506.1	542.1	592.3	620.5	648.3	707.1	776.3	830.5	868.3
32.5°	421.4	451.0	487.0	522.1	571.8	602.7	634.2	702.0	777.7	823.2	841.5
35°	403.2	434.2	463.3	500.7	550.8	581.3	618.2	701.6	771.8	800.0	790.9
37.5°	386.3	412.3	440.1	473.3	524.8	564.5	602.7	689.7	752.2	754.0	702.5
40°	367.7	389.1	412.3	447.4	503.0	542.1	583.6	671.5	716.6	689.7	599.1
42.5°	346.2	365.4	383.6	417.8	478.4	522.1	566.7	648.7	665.1	603.2	508.9
45°	323.5	339.0	355.8	391.8	452.4	495.7	540.3	613.7	596.8	509.3	419.6
47.5°	299.8	313.0	329.4	362.2	424.6	468.8	511.2	563.6	520.7	426.9	351.7
50°	276.1	286.6	302.5	336.2	396.4	436.4	475.6	509.8	449.7	366.3	290.7
52.5°	252.8	261.0	277.4	306.1	364.5	402.7	431.0	444.2	383.1	302.5	252.4
55°	228.2	237.4	248.3	277.4	335.3	363.6	382.2	381.8	318.9	256.5	208.7
57.5°	204.6	212.8	222.3	251.5	298.4	317.5	333.5	325.7	266.1	210.0	179.0
60°	183.6	188.2	198.6	223.2	258.8	275.2	284.3	271.1	217.3	177.2	148.1
62.5°	160.8	165.4	174.0	197.3	219.1	227.8	235.5	218.7	179.5	144.4	126.7
65°	139.9	145.8	151.3	169.9	181.8	192.3	191.3	177.2	140.3	117.5	103.0
67.5°	121.6	123.9	128.5	139.9	145.3	153.1	153.5	137.6	113.0	95.7	87.0
70°	102.0	104.3	107.5	113.0	116.6	118.5	117.5	103.4	85.2	74.7	67.0
72.5°	85.2	84.7	87.0	87.0	90.7	90.2	87.5	76.5	64.7	56.0	51.5
75°	67.0	67.4	67.9	67.0	65.6	63.8	61.5	53.3	45.6	41.5	37.4
77.5°	52.4	51.5	51.9	48.7	46.9	45.1	41.9	37.8	31.4	30.5	28.7
80°	37.4	36.9	36.4	35.1	31.0	29.2	26.9	24.6	23.2	22.3	21.9
82.5°	25.1	25.1	24.1	21.4	19.1	17.8	17.3	16.4	15.0	15.0	14.6
85°	15.0	14.6	13.7	10.9	9.6	9.6	9.6	9.6	8.7	8.7	8.2
87.5°	5.9	5.5	4.1	4.1	3.6	3.6	3.6	3.2	3.2	2.7	2.7
90°	1.5	3.1	4.6	6.9	8.4	9.2	10.0	12.3	14.6	16.9	19.2
92.5°	11.5	16.9	24.5	31.4	39.1	46.0	52.9	77.5	118.1	158.0	142.7
95°	26.1	28.4	36.8	49.9	69.8	84.8	99.7	164.9	279.2	404.9	454.8
97.5°	41.4	42.2	49.1	60.6	80.5	97.0	113.5	177.9	310.6	522.3	699.5
100°	56.8	57.5	62.9	73.6	92.0	107.0	121.9	175.6	289.1	490.8	726.3
102.5°	72.9	74.4	79.0	89.0	105.1	118.5	131.9	178.7	270.7	444.8	676.4
105°	89.0	91.3	95.9	105.1	119.6	131.5	143.4	184.8	263.8	408.8	616.6
107.5°	105.8	108.1	112.7	121.9	135.7	146.8	158.0	194.8	262.3	382.7	563.7
110°	124.2	126.5	130.4	138.8	151.9	162.6	173.3	207.8	266.1	368.9	520.0

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	141.1	143.4	147.3	155.7	168.7	179.0	189.4	220.9	273.8	361.2	490.8
115°	157.2	160.3	164.9	172.6	185.6	196.0	206.3	235.5	282.2	360.5	471.7
117.5°	173.3	177.2	181.0	187.9	202.5	212.0	221.6	250.8	293.0	361.2	458.6
120°	190.2	192.5	196.3	204.0	218.6	228.2	237.8	265.4	305.2	364.3	450.2
122.5°	204.8	207.1	210.9	219.3	233.2	243.6	253.9	280.7	316.7	369.7	444.8
125°	218.6	220.1	224.7	233.2	247.7	258.0	268.4	295.3	329.0	375.0	440.2
127.5°	229.3	231.6	237.0	245.4	261.5	271.8	282.2	308.3	339.0	381.2	437.9
130°	239.3	241.6	248.5	257.7	273.8	284.2	294.5	319.8	349.0	387.3	435.6
132.5°	247.0	250.0	257.7	269.2	285.3	295.2	305.2	329.8	358.2	391.9	434.9
135°	256.2	259.2	267.7	279.2	295.3	305.6	316.0	339.8	365.8	396.5	434.1
137.5°	264.6	267.7	276.1	288.4	304.5	314.1	323.7	346.7	372.0	399.6	432.6
140°	273.0	276.9	284.5	296.8	312.1	321.7	331.3	353.6	376.6	402.6	431.8
142.5°	282.2	285.3	293.7	304.5	319.8	328.6	337.5	358.9	381.2	404.9	430.3
145°	292.2	294.5	301.4	312.9	326.0	334.8	343.6	363.5	384.2	405.7	428.7
147.5°	302.2	303.7	310.6	320.6	333.6	341.3	349.0	367.4	386.5	405.7	426.4
150°	312.1	312.9	319.0	329.0	339.8	346.7	353.6	371.2	387.3	405.7	423.4
152.5°	322.1	322.1	328.3	336.7	345.9	352.4	358.9	373.5	388.8	403.4	419.5
155°	332.1	332.1	336.7	344.4	352.8	358.2	363.5	376.6	388.8	401.9	414.9
157.5°	339.8	340.5	344.4	351.3	358.9	363.2	367.4	378.1	389.6	399.6	411.1
160°	349.0	349.0	352.0	358.2	363.5	367.4	371.2	380.4	389.6	398.0	406.5
162.5°	355.9	355.9	358.2	362.8	367.4	370.4	373.5	381.2	388.8	395.0	401.9
165°	362.8	362.0	363.5	367.4	370.4	373.1	375.8	381.9	387.3	391.9	397.3
167.5°	368.1	367.4	368.1	371.2	373.5	375.4	377.3	381.9	386.5	388.8	392.7
170°	372.7	371.2	372.0	374.3	375.8	376.6	377.3	381.2	384.2	385.8	388.1
172.5°	375.8	375.0	375.0	376.6	377.3	377.7	378.1	381.2	383.5	383.5	384.2
175°	378.1	377.3	376.6	378.1	378.1	378.5	378.9	380.4	381.9	381.2	381.2
177.5°	379.6	378.9	378.1	378.9	378.9	378.9	378.9	379.6	381.2	379.6	378.9
180°	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	561.7	561.7	565.8	569.9	567.7	569.0	574.0	572.2	575.9	575.4	576.8
5°	604.1	609.1	613.2	621.9	623.2	621.9	630.5	632.8	636.9	631.9	634.2
7.5°	651.9	662.4	672.4	685.2	689.3	690.2	694.8	701.1	706.6	696.6	701.6
10°	698.4	714.3	734.8	746.2	756.3	759.9	763.6	767.7	774.0	780.0	775.4
12.5°	748.5	771.8	791.3	811.8	824.1	822.8	833.3	836.0	841.0	842.4	844.2
15°	789.5	822.3	834.6	865.1	867.9	877.0	888.8	899.3	900.7	897.9	897.9
17.5°	828.7	856.9	878.8	903.4	908.4	916.2	931.2	936.2	938.0	937.6	937.6
20°	860.6	879.3	916.2	936.7	944.9	954.9	965.4	971.8	973.1	974.9	972.2
22.5°	881.5	909.8	939.9	956.7	963.6	967.2	974.0	975.9	973.6	974.0	974.5
25°	897.9	925.7	944.0	948.5	948.1	943.5	938.5	929.8	928.9	925.3	918.0
27.5°	902.5	913.0	910.7	892.0	873.3	871.5	841.5	825.1	806.4	809.1	798.6
30°	877.9	864.2	831.9	784.5	764.9	733.0	699.3	664.2	650.6	635.5	663.3
32.5°	817.8	769.0	711.6	650.1	617.3	589.1	553.1	527.6	513.0	500.7	524.4
35°	727.1	651.0	574.9	516.6	489.7	464.2	430.5	417.8	399.5	401.4	403.6
37.5°	610.5	526.6	469.2	411.8	394.1	383.6	359.0	339.4	333.0	331.2	331.2
40°	501.1	432.3	381.3	336.2	322.6	313.9	294.3	285.2	278.4	276.5	278.8
42.5°	414.6	355.8	316.2	286.1	276.5	265.6	257.4	246.0	244.6	241.5	245.6
45°	348.1	297.0	267.4	245.6	237.4	233.3	224.1	217.3	214.6	214.1	217.3
47.5°	295.2	255.6	229.6	215.9	209.6	205.5	197.7	195.0	192.3	193.2	191.8
50°	247.8	218.2	201.4	189.1	185.0	180.9	175.9	173.1	171.8	171.8	171.3
52.5°	212.8	188.2	177.2	165.8	164.0	161.7	156.3	154.4	152.2	151.7	153.5
55°	182.2	165.4	154.4	147.6	145.8	141.2	139.0	136.7	135.3	134.4	134.9
57.5°	155.8	143.1	135.8	129.8	126.7	124.8	120.7	120.3	119.4	119.4	118.9
60°	133.9	124.8	116.2	112.5	110.3	108.0	107.5	104.8	103.4	104.3	103.9
62.5°	113.4	106.1	101.1	97.0	95.7	93.8	92.5	91.6	90.2	90.7	90.7
65°	94.8	88.8	85.2	81.5	81.1	79.3	78.8	77.9	77.9	77.4	78.4
67.5°	77.9	73.8	70.6	68.3	67.0	67.4	65.6	64.2	64.2	63.8	65.1
70°	62.0	59.7	56.5	53.8	51.9	51.9	49.7	49.2	49.2	49.2	48.7
72.5°	47.8	43.7	42.4	41.5	41.5	41.5	40.5	40.5	40.1	40.5	40.1
75°	35.5	35.1	34.2	33.7	33.7	33.3	32.8	32.8	32.8	32.8	32.8
77.5°	27.8	27.8	26.9	26.4	26.4	26.4	26.0	26.0	25.5	25.5	25.5
80°	20.5	20.5	19.6	19.6	19.6	19.1	19.1	19.1	19.6	19.1	19.1
82.5°	14.1	14.1	13.7	14.1	13.7	13.2	13.2	13.2	12.8	13.2	13.2
85°	8.2	8.2	7.7	7.3	7.7	7.7	7.3	7.7	7.3	7.7	7.3
87.5°	3.2	2.7	2.7	2.7	2.3	2.7	2.3	2.3	2.7	2.3	2.7
90°	18.4	19.2	19.9	20.7	21.4	22.2	21.5	22.2	23.0	22.2	23.0
92.5°	106.6	75.9	59.1	51.4	48.7	46.0	44.5	41.4	42.2	40.6	42.2
95°	368.9	276.1	187.1	146.5	132.7	118.9	104.3	97.4	92.0	89.0	92.0
97.5°	723.2	634.3	478.6	377.3	333.6	289.9	238.5	209.4	191.0	182.5	191.0
100°	877.4	904.2	842.1	752.4	698.0	643.5	566.0	510.0	480.1	480.9	480.1
102.5°	885.1	994.0	1007.0	964.0	934.5	905.0	849.0	807.6	783.8	761.6	783.8
105°	836.7	997.0	1073.7	1088.3	1078.4	1068.4	1033.1	1003.9	979.4	975.6	979.4
107.5°	767.7	951.0	1071.4	1131.2	1141.6	1152.0	1147.3	1133.5	1123.6	1115.1	1123.6
110°	703.3	878.9	1020.0	1116.7	1143.6	1170.4	1191.8	1198.0	1196.4	1194.9	1196.4

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	647.3	807.6	952.5	1063.8	1100.2	1136.6	1180.3	1202.6	1210.2	1211.0	1210.2
115°	604.4	746.2	879.7	992.4	1034.2	1076.0	1133.5	1167.3	1182.6	1186.5	1182.6
117.5°	576.0	698.7	816.8	920.3	963.6	1007.0	1066.8	1104.4	1127.4	1132.8	1127.4
120°	554.5	662.6	766.2	858.2	897.0	935.7	996.3	1039.2	1057.6	1062.2	1057.6
122.5°	536.9	634.3	725.5	809.1	844.4	879.7	931.8	969.4	990.1	996.3	990.1
125°	522.3	609.7	693.3	766.9	797.6	828.3	877.4	911.1	930.3	935.7	930.3
127.5°	508.5	587.5	663.4	730.9	759.3	787.7	832.1	861.3	878.9	883.5	878.9
130°	497.7	566.8	635.8	697.9	724.0	750.1	790.7	818.3	834.4	840.6	834.4
132.5°	487.8	547.6	609.7	666.5	691.0	715.6	753.1	780.7	794.6	798.4	794.6
135°	479.3	530.7	585.2	635.0	656.8	678.7	716.3	739.3	753.1	758.5	753.1
137.5°	471.7	514.6	560.6	605.1	624.7	644.2	676.4	700.2	711.7	716.3	711.7
140°	464.8	500.8	539.9	576.7	593.2	609.7	638.9	660.3	672.6	671.8	672.6
142.5°	458.6	487.8	520.0	550.7	564.5	578.3	602.1	620.5	631.2	630.4	631.2
145°	453.3	477.8	503.1	527.7	538.8	549.9	569.1	585.2	591.3	592.8	591.3
147.5°	447.9	469.4	490.1	510.8	518.8	526.9	542.2	553.7	559.9	560.6	559.9
150°	442.5	460.2	477.8	493.9	501.2	508.5	520.0	528.4	533.0	533.0	533.0
152.5°	436.4	451.7	466.3	480.1	485.8	491.6	500.0	507.7	510.0	510.0	510.0
155°	430.3	443.3	455.6	467.1	471.7	476.3	483.2	489.3	490.8	491.6	490.8
157.5°	423.4	434.1	444.8	454.0	457.8	461.7	467.8	472.4	474.0	474.0	474.0
160°	416.5	426.4	434.9	442.5	445.2	447.9	453.3	457.9	457.9	457.1	457.9
162.5°	409.5	417.2	424.1	431.0	433.3	435.6	438.7	442.5	442.5	441.8	442.5
165°	403.4	409.5	414.1	419.5	421.4	423.4	426.4	429.5	428.7	428.7	428.7
167.5°	397.3	402.6	406.5	409.5	411.0	412.6	414.1	416.5	415.7	415.7	415.7
170°	391.9	395.7	398.0	401.1	401.8	402.6	403.4	404.9	404.2	404.2	404.2
172.5°	386.5	389.6	391.1	393.4	393.8	394.2	394.2	395.7	394.2	393.4	394.2
175°	382.7	384.2	385.0	386.5	386.5	386.5	386.5	387.3	386.5	385.8	386.5
177.5°	379.6	380.4	381.2	381.9	381.9	381.9	381.2	381.9	380.4	380.4	380.4
180°	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	574.5	571.8	569.9	568.6	567.2	571.3	565.8	559.9	555.8	553.1	552.2
5°	634.6	628.7	623.7	619.6	620.5	620.5	610.9	600.5	591.3	586.3	580.9
7.5°	704.3	697.9	687.9	685.6	683.8	672.4	662.9	643.7	632.3	621.0	610.9
10°	773.6	765.4	755.8	752.6	748.1	733.9	719.4	694.8	680.6	659.7	646.5
12.5°	838.3	828.2	818.7	816.4	809.6	797.3	772.2	746.7	722.5	700.2	677.0
15°	892.5	889.7	875.2	866.1	851.0	834.2	828.7	794.1	763.6	740.3	698.4
17.5°	938.0	925.3	911.6	905.7	899.8	880.2	860.6	825.1	792.3	758.1	731.2
20°	974.5	960.4	950.8	942.1	939.4	917.1	886.1	854.7	818.7	780.4	745.3
22.5°	976.3	974.5	968.1	963.1	957.6	943.0	918.4	879.3	841.0	799.1	753.1
25°	938.5	935.8	954.0	949.4	953.1	947.6	934.4	901.6	856.9	807.7	761.3
27.5°	824.6	852.4	881.1	891.1	897.9	917.5	923.9	905.7	869.7	817.3	765.4
30°	669.7	706.6	753.1	778.1	797.3	833.7	881.1	887.0	870.2	828.2	764.5
32.5°	525.7	559.5	596.8	626.4	651.9	726.6	790.4	836.4	844.6	822.8	766.7
35°	423.7	438.3	473.8	502.0	536.7	600.5	675.6	749.9	800.0	802.7	759.9
37.5°	349.4	357.2	388.2	404.1	424.6	480.6	550.8	647.8	725.7	762.6	740.8
40°	289.3	307.1	324.8	333.9	348.5	387.2	454.7	530.7	627.3	695.7	711.2
42.5°	251.0	258.8	270.2	282.9	292.0	325.7	370.8	440.5	527.6	622.8	665.6
45°	221.4	224.1	236.0	244.2	253.8	277.4	309.3	367.7	444.2	538.0	610.9
47.5°	196.8	202.3	208.7	213.7	220.0	238.3	265.6	308.0	375.4	459.2	537.6
50°	174.9	178.1	186.3	188.6	193.2	205.9	226.9	259.2	314.8	381.8	462.9
52.5°	154.4	160.4	163.6	166.7	170.8	181.3	195.0	221.4	263.3	326.2	395.0
55°	138.5	140.3	144.9	147.6	150.8	158.1	169.9	189.5	222.3	272.4	337.6
57.5°	123.0	123.0	127.6	129.8	133.0	138.5	149.0	164.0	187.7	225.1	284.7
60°	106.6	107.1	110.7	113.4	114.4	119.8	128.5	140.3	158.5	185.9	234.6
62.5°	92.0	94.3	96.1	97.0	100.2	103.4	110.7	118.9	131.7	155.8	190.4
65°	79.7	80.2	81.5	82.5	83.8	87.5	92.9	98.4	109.3	127.1	155.4
67.5°	65.6	67.4	69.2	69.2	70.6	72.4	77.9	82.5	90.7	101.1	120.3
70°	49.2	50.1	52.8	54.2	56.0	59.2	62.0	64.7	71.1	78.8	93.4
72.5°	41.0	41.0	41.9	42.4	42.4	44.6	48.7	51.5	54.7	60.1	70.2
75°	32.8	32.8	34.2	33.7	34.6	35.5	36.0	37.8	39.6	43.7	49.7
77.5°	26.0	26.4	26.4	26.9	26.9	27.3	27.8	28.7	29.6	31.9	34.6
80°	19.1	19.6	19.6	20.0	20.0	20.5	21.0	21.4	22.3	23.2	24.6
82.5°	13.2	13.7	13.7	14.1	13.7	14.1	14.6	14.6	15.0	15.9	16.4
85°	7.7	7.7	8.2	7.7	7.7	7.7	8.2	8.2	8.7	10.0	10.0
87.5°	2.3	2.7	2.3	2.7	2.7	2.7	2.7	3.2	3.2	3.6	4.1
90°	22.2	21.5	22.2	21.4	20.7	19.9	19.2	18.4	19.2	16.9	14.6
92.5°	41.4	44.5	46.0	48.7	51.4	59.1	75.9	106.6	142.7	158.0	118.1
95°	97.4	104.3	118.9	132.7	146.5	187.1	276.1	368.9	454.8	404.9	279.2
97.5°	209.4	238.5	289.9	333.6	377.3	478.6	634.3	723.2	699.5	522.3	310.6
100°	510.0	566.0	643.5	698.0	752.4	842.1	904.2	877.4	726.3	490.8	289.1
102.5°	807.6	849.0	905.0	934.5	964.0	1007.0	994.0	885.1	676.4	444.8	270.7
105°	1003.9	1033.1	1068.4	1078.4	1088.3	1073.7	997.0	836.7	616.6	408.8	263.8
107.5°	1133.5	1147.3	1152.0	1141.6	1131.2	1071.4	951.0	767.7	563.7	382.7	262.3
110°	1198.0	1191.8	1170.4	1143.6	1116.7	1020.0	878.9	703.3	520.0	368.9	266.1

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1202.6	1180.3	1136.6	1100.2	1063.8	952.5	807.6	647.3	490.8	361.2	273.8
115°	1167.3	1133.5	1076.0	1034.2	992.4	879.7	746.2	604.4	471.7	360.5	282.2
117.5°	1104.4	1066.8	1007.0	963.6	920.3	816.8	698.7	576.0	458.6	361.2	293.0
120°	1039.2	996.3	935.7	897.0	858.2	766.2	662.6	554.5	450.2	364.3	305.2
122.5°	969.4	931.8	879.7	844.4	809.1	725.5	634.3	536.9	444.8	369.7	316.7
125°	911.1	877.4	828.3	797.6	766.9	693.3	609.7	522.3	440.2	375.0	329.0
127.5°	861.3	832.1	787.7	759.3	730.9	663.4	587.5	508.5	437.9	381.2	339.0
130°	818.3	790.7	750.1	724.0	697.9	635.8	566.8	497.7	435.6	387.3	349.0
132.5°	780.7	753.1	715.6	691.0	666.5	609.7	547.6	487.8	434.9	391.9	358.2
135°	739.3	716.3	678.7	656.8	635.0	585.2	530.7	479.3	434.1	396.5	365.8
137.5°	700.2	676.4	644.2	624.7	605.1	560.6	514.6	471.7	432.6	399.6	372.0
140°	660.3	638.9	609.7	593.2	576.7	539.9	500.8	464.8	431.8	402.6	376.6
142.5°	620.5	602.1	578.3	564.5	550.7	520.0	487.8	458.6	430.3	404.9	381.2
145°	585.2	569.1	549.9	538.8	527.7	503.1	477.8	453.3	428.7	405.7	384.2
147.5°	553.7	542.2	526.9	518.8	510.8	490.1	469.4	447.9	426.4	405.7	386.5
150°	528.4	520.0	508.5	501.2	493.9	477.8	460.2	442.5	423.4	405.7	387.3
152.5°	507.7	500.0	491.6	485.8	480.1	466.3	451.7	436.4	419.5	403.4	388.8
155°	489.3	483.2	476.3	471.7	467.1	455.6	443.3	430.3	414.9	401.9	388.8
157.5°	472.4	467.8	461.7	457.8	454.0	444.8	434.1	423.4	411.1	399.6	389.6
160°	457.9	453.3	447.9	445.2	442.5	434.9	426.4	416.5	406.5	398.0	389.6
162.5°	442.5	438.7	435.6	433.3	431.0	424.1	417.2	409.5	401.9	395.0	388.8
165°	429.5	426.4	423.4	421.4	419.5	414.1	409.5	403.4	397.3	391.9	387.3
167.5°	416.5	414.1	412.6	411.0	409.5	406.5	402.6	397.3	392.7	388.8	386.5
170°	404.9	403.4	402.6	401.8	401.1	398.0	395.7	391.9	388.1	385.8	384.2
172.5°	395.7	394.2	394.2	393.8	393.4	391.1	389.6	386.5	384.2	383.5	383.5
175°	387.3	386.5	386.5	386.5	386.5	385.0	384.2	382.7	381.2	381.2	381.9
177.5°	381.9	381.2	381.9	381.9	381.9	381.2	380.4	379.6	378.9	379.6	381.2
180°	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	550.8	548.5	546.2	546.2	541.2	536.7	534.4	535.3	532.6	528.9	525.3
5°	574.9	565.8	564.0	559.0	552.2	542.6	537.6	533.0	527.6	520.3	513.4
7.5°	597.3	585.4	579.0	574.0	560.8	547.6	536.7	529.4	519.8	508.9	500.7
10°	626.4	604.6	597.7	586.3	567.7	549.0	536.2	524.4	511.2	498.4	487.5
12.5°	649.7	624.6	611.8	600.5	576.3	552.6	531.2	516.6	500.7	486.6	472.4
15°	676.1	647.8	625.5	611.8	581.3	552.6	528.5	508.0	490.2	472.9	460.6
17.5°	688.8	653.3	643.3	623.7	579.5	550.8	521.2	499.3	477.9	457.9	443.3
20°	708.9	667.4	642.4	629.2	590.0	547.6	513.0	487.9	465.6	444.2	428.7
22.5°	710.2	665.1	648.7	623.7	575.4	538.0	505.7	475.2	449.2	429.2	413.2
25°	707.1	661.0	638.3	618.2	578.1	532.6	491.1	461.0	435.5	412.3	393.6
27.5°	705.7	649.2	627.8	607.7	562.6	516.6	482.5	448.3	419.1	398.6	379.5
30°	703.9	636.4	610.5	587.2	545.8	504.3	463.3	433.7	405.9	380.0	360.8
32.5°	692.0	619.1	592.7	568.1	523.5	482.0	449.7	418.2	388.2	364.0	346.7
35°	688.4	603.2	568.6	542.1	498.4	461.5	427.3	401.4	373.1	349.0	328.5
37.5°	677.9	586.8	549.4	515.7	470.2	435.1	410.0	384.1	356.7	330.8	314.3
40°	659.7	567.7	525.3	490.7	443.7	408.2	385.0	365.8	339.0	315.7	295.7
42.5°	632.8	548.1	502.5	466.1	414.1	380.9	361.7	343.5	320.7	296.6	280.2
45°	601.8	522.1	479.7	439.2	386.3	354.0	333.9	323.0	302.0	281.5	262.4
47.5°	559.5	495.2	453.3	411.4	357.6	326.2	310.2	299.3	284.7	262.4	246.9
50°	506.1	460.6	421.0	383.6	329.4	299.3	283.4	275.2	262.9	246.9	231.9
52.5°	446.9	420.5	387.7	353.1	300.7	272.4	257.9	251.5	242.4	227.3	214.6
55°	387.2	375.9	353.5	319.4	270.6	247.4	234.6	226.4	219.6	208.7	197.7
57.5°	333.9	328.5	313.0	286.6	245.6	221.4	210.5	205.0	199.5	191.3	180.4
60°	278.8	284.7	268.8	255.6	218.2	197.3	187.7	181.8	179.0	171.8	164.9
62.5°	231.0	236.4	227.3	217.3	190.9	172.2	166.3	160.8	159.0	152.6	145.8
65°	187.7	194.5	187.7	182.2	166.3	150.8	143.5	140.8	139.0	134.9	129.4
67.5°	149.4	156.3	153.1	146.2	141.2	128.5	124.4	121.6	120.7	117.5	113.0
70°	112.5	122.1	123.0	118.9	114.4	108.4	105.7	104.8	102.5	99.8	97.0
72.5°	81.1	92.0	92.5	92.5	89.7	89.7	87.0	85.6	85.6	82.9	79.7
75°	59.7	67.0	67.9	68.8	70.2	71.5	69.7	69.7	69.2	66.5	65.1
77.5°	39.6	46.0	48.3	51.5	53.3	53.3	54.2	55.1	54.2	52.8	51.9
80°	25.5	30.1	32.8	34.6	37.4	38.7	40.1	40.5	39.6	39.2	37.8
82.5°	16.9	18.2	19.6	21.9	25.1	27.3	27.3	26.9	27.8	27.3	26.9
85°	9.6	10.5	10.9	11.4	13.2	15.5	15.9	16.4	17.3	16.4	15.5
87.5°	3.6	4.1	4.1	4.1	5.0	5.5	6.8	8.7	8.2	7.3	7.3
90°	12.3	10.0	9.2	8.4	6.9	4.6	3.1	1.5	3.1	4.6	6.9
92.5°	77.5	52.9	46.0	39.1	31.4	24.5	16.9	11.5	16.9	24.5	31.4
95°	164.9	99.7	84.8	69.8	49.9	36.8	28.4	26.1	28.4	36.8	49.9
97.5°	177.9	113.5	97.0	80.5	60.6	49.1	42.2	41.4	42.2	49.1	60.6
100°	175.6	121.9	107.0	92.0	73.6	62.9	57.5	56.8	57.5	62.9	73.6
102.5°	178.7	131.9	118.5	105.1	89.0	79.0	74.4	72.9	74.4	79.0	89.0
105°	184.8	143.4	131.5	119.6	105.1	95.9	91.3	89.0	91.3	95.9	105.1
107.5°	194.8	158.0	146.8	135.7	121.9	112.7	108.1	105.8	108.1	112.7	121.9
110°	207.8	173.3	162.6	151.9	138.8	130.4	126.5	124.2	126.5	130.4	138.8

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	220.9	189.4	179.0	168.7	155.7	147.3	143.4	141.1	143.4	147.3	155.7
115°	235.5	206.3	196.0	185.6	172.6	164.9	160.3	157.2	160.3	164.9	172.6
117.5°	250.8	221.6	212.0	202.5	187.9	181.0	177.2	173.3	177.2	181.0	187.9
120°	265.4	237.8	228.2	218.6	204.0	196.3	192.5	190.2	192.5	196.3	204.0
122.5°	280.7	253.9	243.6	233.2	219.3	210.9	207.1	204.8	207.1	210.9	219.3
125°	295.3	268.4	258.0	247.7	233.2	224.7	220.1	218.6	220.1	224.7	233.2
127.5°	308.3	282.2	271.8	261.5	245.4	237.0	231.6	229.3	231.6	237.0	245.4
130°	319.8	294.5	284.2	273.8	257.7	248.5	241.6	239.3	241.6	248.5	257.7
132.5°	329.8	305.2	295.2	285.3	269.2	257.7	250.0	247.0	250.0	257.7	269.2
135°	339.8	316.0	305.6	295.3	279.2	267.7	259.2	256.2	259.2	267.7	279.2
137.5°	346.7	323.7	314.1	304.5	288.4	276.1	267.7	264.6	267.7	276.1	288.4
140°	353.6	331.3	321.7	312.1	296.8	284.5	276.9	273.0	276.9	284.5	296.8
142.5°	358.9	337.5	328.6	319.8	304.5	293.7	285.3	282.2	285.3	293.7	304.5
145°	363.5	343.6	334.8	326.0	312.9	301.4	294.5	292.2	294.5	301.4	312.9
147.5°	367.4	349.0	341.3	333.6	320.6	310.6	303.7	302.2	303.7	310.6	320.6
150°	371.2	353.6	346.7	339.8	329.0	319.0	312.9	312.1	312.9	319.0	329.0
152.5°	373.5	358.9	352.4	345.9	336.7	328.3	322.1	322.1	322.1	328.3	336.7
155°	376.6	363.5	358.2	352.8	344.4	336.7	332.1	332.1	332.1	336.7	344.4
157.5°	378.1	367.4	363.2	358.9	351.3	344.4	340.5	339.8	340.5	344.4	351.3
160°	380.4	371.2	367.4	363.5	358.2	352.0	349.0	349.0	349.0	352.0	358.2
162.5°	381.2	373.5	370.4	367.4	362.8	358.2	355.9	355.9	355.9	358.2	362.8
165°	381.9	375.8	373.1	370.4	367.4	363.5	362.0	362.8	362.0	363.5	367.4
167.5°	381.9	377.3	375.4	373.5	371.2	368.1	367.4	368.1	367.4	368.1	371.2
170°	381.2	377.3	376.6	375.8	374.3	372.0	371.2	372.7	371.2	372.0	374.3
172.5°	381.2	378.1	377.7	377.3	376.6	375.0	375.0	375.8	375.0	375.0	376.6
175°	380.4	378.9	378.5	378.1	378.1	376.6	377.3	378.1	377.3	376.6	378.1
177.5°	379.6	378.9	378.9	378.9	378.9	378.1	378.9	379.6	378.9	378.1	378.9
180°	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	525.3	523.0	522.1	519.8	514.3	510.7	506.6	503.9	504.3	502.0	503.4
5°	508.9	508.4	505.2	500.7	492.9	488.8	481.5	477.9	476.1	476.5	473.8
7.5°	495.2	491.1	488.8	481.5	474.3	465.6	459.7	456.5	453.8	451.0	449.2
10°	479.7	476.1	472.4	464.7	454.7	446.5	438.3	435.1	431.0	429.2	427.8
12.5°	463.3	461.0	456.5	447.4	436.0	428.2	418.7	416.9	411.4	407.7	406.8
15°	448.3	446.9	438.7	428.2	416.9	409.1	400.9	395.4	386.3	388.2	385.0
17.5°	432.3	426.4	421.4	407.3	401.8	390.0	380.4	377.7	371.3	367.2	363.1
20°	414.6	410.9	404.6	395.4	382.2	368.6	361.3	356.7	353.1	346.7	344.9
22.5°	397.7	393.2	387.7	375.9	364.5	353.1	343.1	339.0	334.4	329.8	327.1
25°	384.5	377.7	371.8	357.2	345.8	336.2	329.8	323.0	316.6	313.9	313.0
27.5°	364.0	359.9	354.0	340.3	329.8	319.4	313.4	308.9	302.0	298.9	296.1
30°	350.8	342.6	335.8	324.8	314.3	303.0	297.5	292.0	287.9	283.8	280.6
32.5°	333.0	326.7	321.2	310.2	299.8	289.3	283.4	275.2	272.9	269.7	266.1
35°	315.7	311.6	305.7	293.8	282.5	275.2	268.8	261.0	258.3	256.0	252.8
37.5°	299.3	293.4	289.3	277.9	267.9	259.2	254.2	247.8	246.0	243.3	241.0
40°	285.2	279.3	275.2	263.8	253.3	244.2	241.0	234.6	231.9	228.7	227.3
42.5°	269.2	264.2	258.8	250.6	239.6	230.5	224.1	220.5	216.9	215.5	212.8
45°	252.4	247.8	243.7	234.6	223.2	216.9	211.4	206.4	203.6	201.4	199.5
47.5°	237.8	233.7	228.2	218.2	209.1	203.2	197.7	192.7	190.0	187.2	185.0
50°	221.0	218.7	212.8	203.2	194.5	187.7	182.7	178.1	176.3	173.1	169.5
52.5°	205.9	201.8	196.8	189.1	181.3	173.1	166.3	163.6	160.4	158.5	155.4
55°	188.2	185.4	180.0	173.1	164.9	158.1	153.1	149.4	145.3	143.5	139.4
57.5°	173.1	168.1	165.4	156.7	149.0	142.1	138.5	134.9	130.3	127.6	125.7
60°	156.7	152.2	148.1	140.8	135.3	128.0	122.6	119.4	116.2	112.5	110.7
62.5°	140.8	137.1	132.1	126.2	119.4	113.4	109.3	104.8	103.0	99.3	97.9
65°	123.5	120.7	116.6	109.8	104.3	99.3	95.2	91.6	89.7	88.4	87.5
67.5°	108.0	104.3	101.6	95.7	89.7	85.6	83.4	81.1	78.8	77.4	76.1
70°	92.0	89.3	86.6	81.1	77.0	73.3	71.5	69.7	68.3	67.0	65.6
72.5°	75.6	74.3	71.5	67.9	64.7	62.0	60.6	58.3	56.9	54.7	53.8
75°	62.4	60.1	58.8	55.6	52.8	50.6	48.7	46.0	44.2	43.3	42.8
77.5°	49.2	48.3	46.5	43.7	42.4	40.1	37.4	36.4	35.5	35.5	35.1
80°	36.9	35.5	34.2	31.9	30.5	28.7	28.7	28.7	28.2	28.7	28.2
82.5°	25.1	24.1	23.2	21.9	21.4	21.4	21.9	21.9	21.9	21.9	21.9
85°	14.6	14.6	14.6	15.0	14.6	14.6	15.0	15.5	15.0	15.0	14.6
87.5°	6.8	6.8	7.3	7.3	7.7	7.7	7.7	7.7	7.7	7.7	8.2
90°	8.4	9.2	10.0	12.3	14.6	16.9	19.2	18.4	19.2	19.9	20.7
92.5°	39.1	46.0	52.9	77.5	118.1	158.0	142.7	106.6	75.9	59.1	51.4
95°	69.8	84.8	99.7	164.9	279.2	404.9	454.8	368.9	276.1	187.1	146.5
97.5°	80.5	97.0	113.5	177.9	310.6	522.3	699.5	723.2	634.3	478.6	377.3
100°	92.0	107.0	121.9	175.6	289.1	490.8	726.3	877.4	904.2	842.1	752.4
102.5°	105.1	118.5	131.9	178.7	270.7	444.8	676.4	885.1	994.0	1007.0	964.0
105°	119.6	131.5	143.4	184.8	263.8	408.8	616.6	836.7	997.0	1073.7	1088.3
107.5°	135.7	146.8	158.0	194.8	262.3	382.7	563.7	767.7	951.0	1071.4	1131.2
110°	151.9	162.6	173.3	207.8	266.1	368.9	520.0	703.3	878.9	1020.0	1116.7

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	168.7	179.0	189.4	220.9	273.8	361.2	490.8	647.3	807.6	952.5	1063.8
115°	185.6	196.0	206.3	235.5	282.2	360.5	471.7	604.4	746.2	879.7	992.4
117.5°	202.5	212.0	221.6	250.8	293.0	361.2	458.6	576.0	698.7	816.8	920.3
120°	218.6	228.2	237.8	265.4	305.2	364.3	450.2	554.5	662.6	766.2	858.2
122.5°	233.2	243.6	253.9	280.7	316.7	369.7	444.8	536.9	634.3	725.5	809.1
125°	247.7	258.0	268.4	295.3	329.0	375.0	440.2	522.3	609.7	693.3	766.9
127.5°	261.5	271.8	282.2	308.3	339.0	381.2	437.9	508.5	587.5	663.4	730.9
130°	273.8	284.2	294.5	319.8	349.0	387.3	435.6	497.7	566.8	635.8	697.9
132.5°	285.3	295.2	305.2	329.8	358.2	391.9	434.9	487.8	547.6	609.7	666.5
135°	295.3	305.6	316.0	339.8	365.8	396.5	434.1	479.3	530.7	585.2	635.0
137.5°	304.5	314.1	323.7	346.7	372.0	399.6	432.6	471.7	514.6	560.6	605.1
140°	312.1	321.7	331.3	353.6	376.6	402.6	431.8	464.8	500.8	539.9	576.7
142.5°	319.8	328.6	337.5	358.9	381.2	404.9	430.3	458.6	487.8	520.0	550.7
145°	326.0	334.8	343.6	363.5	384.2	405.7	428.7	453.3	477.8	503.1	527.7
147.5°	333.6	341.3	349.0	367.4	386.5	405.7	426.4	447.9	469.4	490.1	510.8
150°	339.8	346.7	353.6	371.2	387.3	405.7	423.4	442.5	460.2	477.8	493.9
152.5°	345.9	352.4	358.9	373.5	388.8	403.4	419.5	436.4	451.7	466.3	480.1
155°	352.8	358.2	363.5	376.6	388.8	401.9	414.9	430.3	443.3	455.6	467.1
157.5°	358.9	363.2	367.4	378.1	389.6	399.6	411.1	423.4	434.1	444.8	454.0
160°	363.5	367.4	371.2	380.4	389.6	398.0	406.5	416.5	426.4	434.9	442.5
162.5°	367.4	370.4	373.5	381.2	388.8	395.0	401.9	409.5	417.2	424.1	431.0
165°	370.4	373.1	375.8	381.9	387.3	391.9	397.3	403.4	409.5	414.1	419.5
167.5°	373.5	375.4	377.3	381.9	386.5	388.8	392.7	397.3	402.6	406.5	409.5
170°	375.8	376.6	377.3	381.2	384.2	385.8	388.1	391.9	395.7	398.0	401.1
172.5°	377.3	377.7	378.1	381.2	383.5	383.5	384.2	386.5	389.6	391.1	393.4
175°	378.1	378.5	378.9	380.4	381.9	381.2	381.2	382.7	384.2	385.0	386.5
177.5°	378.9	378.9	378.9	379.6	381.2	379.6	378.9	379.6	380.4	381.2	381.9
180°	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	503.0	503.4	502.0	499.3	498.9	499.8	502.5	501.6	499.3	503.4	499.8
5°	475.2	472.9	472.0	472.9	470.2	468.8	471.5	470.2	471.5	472.0	473.3
7.5°	448.3	448.7	446.0	446.5	442.8	443.7	443.7	443.7	445.1	446.0	447.8
10°	425.1	426.0	422.8	423.2	420.5	418.7	420.0	422.8	422.8	422.8	423.7
12.5°	406.4	402.3	400.0	399.5	396.4	395.4	398.2	399.1	401.4	401.4	402.7
15°	383.1	382.2	380.4	380.4	372.7	374.5	375.4	378.6	383.1	379.5	380.4
17.5°	362.2	359.9	357.6	356.7	355.8	353.1	356.7	356.3	359.0	359.5	360.8
20°	343.5	341.7	337.1	337.6	338.5	334.4	336.7	336.7	339.4	342.1	345.3
22.5°	325.3	323.5	321.2	322.1	319.4	318.4	318.4	320.7	323.9	326.2	325.7
25°	311.2	308.0	306.6	305.2	303.9	304.8	303.4	305.7	308.0	309.3	308.0
27.5°	295.2	293.8	291.1	289.7	287.5	288.4	289.3	291.1	292.5	292.5	293.8
30°	279.7	277.9	277.0	275.6	275.6	273.8	274.3	276.1	277.4	278.8	280.6
32.5°	264.7	263.3	262.0	262.0	261.0	260.6	260.1	262.9	262.9	265.6	265.6
35°	252.4	250.1	250.1	247.8	248.7	248.3	247.4	249.2	249.7	251.5	251.0
37.5°	238.7	238.7	237.8	235.5	233.7	234.2	236.4	236.4	237.8	237.4	238.7
40°	225.1	224.1	224.1	222.8	222.3	221.9	222.3	222.8	225.1	224.6	225.1
42.5°	211.4	211.8	209.6	209.6	209.6	208.2	208.7	209.1	210.0	210.9	212.3
45°	198.2	197.3	196.8	195.9	195.0	195.4	195.0	196.8	196.4	197.3	198.6
47.5°	184.1	182.7	182.2	180.4	180.4	181.3	180.9	182.2	182.7	184.1	183.1
50°	170.4	168.6	167.2	167.7	164.9	165.8	165.8	167.2	168.6	169.0	169.9
52.5°	154.4	154.0	153.5	151.3	150.8	150.3	150.8	151.3	153.1	154.4	154.9
55°	139.0	138.5	135.8	134.9	133.5	133.5	134.4	134.9	138.0	138.5	140.3
57.5°	124.8	123.5	120.3	119.8	119.8	119.8	118.5	120.3	121.2	123.5	123.5
60°	109.3	109.3	106.6	106.6	107.1	106.6	106.6	107.1	107.1	108.9	109.8
62.5°	97.0	96.6	96.6	95.7	95.2	95.7	95.2	95.2	95.7	97.0	98.4
65°	86.1	85.6	85.2	84.7	83.8	83.8	84.3	85.2	85.2	86.1	86.6
67.5°	75.6	75.6	74.7	74.7	74.3	73.8	74.3	73.8	75.6	75.6	76.1
70°	65.1	64.7	63.3	62.9	61.5	62.0	62.0	63.3	63.8	64.7	65.6
72.5°	52.4	52.4	51.5	50.6	51.0	50.1	50.1	50.6	50.6	51.9	52.4
75°	43.3	42.4	41.9	42.4	41.9	42.8	41.9	41.9	42.8	42.8	42.8
77.5°	35.5	35.5	35.1	35.1	35.5	35.1	35.5	35.5	35.5	35.1	35.5
80°	29.2	28.7	28.7	28.7	28.2	28.2	28.2	28.2	28.2	28.2	28.2
82.5°	21.9	21.9	21.4	21.9	21.9	21.4	21.9	21.4	21.4	21.9	21.9
85°	14.6	15.5	14.6	14.6	15.0	15.0	15.5	15.0	15.5	14.6	15.0
87.5°	7.7	8.2	8.2	7.7	7.7	8.2	8.2	8.2	8.7	7.7	8.2
90°	21.4	22.2	21.5	22.2	23.0	22.2	23.0	22.2	21.5	22.2	21.4
92.5°	48.7	46.0	44.5	41.4	42.2	40.6	42.2	41.4	44.5	46.0	48.7
95°	132.7	118.9	104.3	97.4	92.0	89.0	92.0	97.4	104.3	118.9	132.7
97.5°	333.6	289.9	238.5	209.4	191.0	182.5	191.0	209.4	238.5	289.9	333.6
100°	698.0	643.5	566.0	510.0	480.1	480.9	480.1	510.0	566.0	643.5	698.0
102.5°	934.5	905.0	849.0	807.6	783.8	761.6	783.8	807.6	849.0	905.0	934.5
105°	1078.4	1068.4	1033.1	1003.9	979.4	975.6	979.4	1003.9	1033.1	1068.4	1078.4
107.5°	1141.6	1152.0	1147.3	1133.5	1123.6	1115.1	1123.6	1133.5	1147.3	1152.0	1141.6
110°	1143.6	1170.4	1191.8	1198.0	1196.4	1194.9	1196.4	1198.0	1191.8	1170.4	1143.6

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1100.2	1136.6	1180.3	1202.6	1210.2	1211.0	1210.2	1202.6	1180.3	1136.6	1100.2
115°	1034.2	1076.0	1133.5	1167.3	1182.6	1186.5	1182.6	1167.3	1133.5	1076.0	1034.2
117.5°	963.6	1007.0	1066.8	1104.4	1127.4	1132.8	1127.4	1104.4	1066.8	1007.0	963.6
120°	897.0	935.7	996.3	1039.2	1057.6	1062.2	1057.6	1039.2	996.3	935.7	897.0
122.5°	844.4	879.7	931.8	969.4	990.1	996.3	990.1	969.4	931.8	879.7	844.4
125°	797.6	828.3	877.4	911.1	930.3	935.7	930.3	911.1	877.4	828.3	797.6
127.5°	759.3	787.7	832.1	861.3	878.9	883.5	878.9	861.3	832.1	787.7	759.3
130°	724.0	750.1	790.7	818.3	834.4	840.6	834.4	818.3	790.7	750.1	724.0
132.5°	691.0	715.6	753.1	780.7	794.6	798.4	794.6	780.7	753.1	715.6	691.0
135°	656.8	678.7	716.3	739.3	753.1	758.5	753.1	739.3	716.3	678.7	656.8
137.5°	624.7	644.2	676.4	700.2	711.7	716.3	711.7	700.2	676.4	644.2	624.7
140°	593.2	609.7	638.9	660.3	672.6	671.8	672.6	660.3	638.9	609.7	593.2
142.5°	564.5	578.3	602.1	620.5	631.2	630.4	631.2	620.5	602.1	578.3	564.5
145°	538.8	549.9	569.1	585.2	591.3	592.8	591.3	585.2	569.1	549.9	538.8
147.5°	518.8	526.9	542.2	553.7	559.9	560.6	559.9	553.7	542.2	526.9	518.8
150°	501.2	508.5	520.0	528.4	533.0	533.0	533.0	528.4	520.0	508.5	501.2
152.5°	485.8	491.6	500.0	507.7	510.0	510.0	510.0	507.7	500.0	491.6	485.8
155°	471.7	476.3	483.2	489.3	490.8	491.6	490.8	489.3	483.2	476.3	471.7
157.5°	457.8	461.7	467.8	472.4	474.0	474.0	474.0	472.4	467.8	461.7	457.8
160°	445.2	447.9	453.3	457.9	457.9	457.1	457.9	457.9	453.3	447.9	445.2
162.5°	433.3	435.6	438.7	442.5	442.5	441.8	442.5	442.5	438.7	435.6	433.3
165°	421.4	423.4	426.4	429.5	428.7	428.7	428.7	429.5	426.4	423.4	421.4
167.5°	411.0	412.6	414.1	416.5	415.7	415.7	415.7	416.5	414.1	412.6	411.0
170°	401.8	402.6	403.4	404.9	404.2	404.2	404.2	404.9	403.4	402.6	401.8
172.5°	393.8	394.2	394.2	395.7	394.2	393.4	394.2	395.7	394.2	394.2	393.8
175°	386.5	386.5	386.5	387.3	386.5	385.8	386.5	387.3	386.5	386.5	386.5
177.5°	381.9	381.9	381.2	381.9	380.4	380.4	380.4	381.9	381.2	381.9	381.9
180°	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	503.4	505.2	503.4	499.8	503.4	505.7	508.0	511.6	513.4	513.4	516.2
5°	474.7	478.4	477.0	476.1	479.7	482.0	485.6	490.2	495.2	498.4	502.0
7.5°	449.2	451.5	453.8	453.8	457.4	462.4	467.9	473.3	479.7	484.3	487.0
10°	426.9	428.7	430.1	431.9	437.4	442.8	450.1	456.9	462.4	467.4	472.0
12.5°	405.5	408.2	411.4	412.8	416.9	423.7	430.5	438.7	447.4	452.4	456.9
15°	385.0	386.3	390.0	394.1	397.7	405.0	413.7	422.3	429.6	437.4	441.5
17.5°	364.0	364.5	374.0	371.8	383.6	390.4	395.0	403.2	415.0	421.4	427.8
20°	343.5	348.1	352.2	354.4	360.8	368.6	381.8	388.2	397.7	403.6	409.1
22.5°	327.6	334.4	334.4	339.9	343.1	350.3	359.9	372.2	382.7	386.8	394.5
25°	313.4	316.6	322.1	323.9	329.8	336.2	342.6	355.8	367.2	372.7	378.1
27.5°	295.2	299.3	306.6	306.6	314.3	321.2	328.9	337.6	349.0	356.7	362.6
30°	281.1	285.2	288.4	293.4	296.6	303.0	316.6	323.0	333.0	339.9	347.2
32.5°	267.9	271.1	273.8	279.3	282.9	290.2	297.5	308.9	317.5	323.9	331.7
35°	253.3	256.5	260.1	264.2	269.7	276.5	283.4	292.9	301.6	307.5	313.9
37.5°	239.6	241.9	247.4	250.1	254.7	261.0	269.7	279.7	287.5	292.0	298.4
40°	226.4	228.2	232.3	237.4	240.5	245.6	254.7	263.3	272.9	278.4	283.4
42.5°	212.3	214.6	218.2	223.2	228.2	233.7	238.7	248.7	257.4	262.0	267.4
45°	200.0	201.4	204.1	209.1	214.1	218.2	226.0	235.1	243.3	246.9	252.8
47.5°	185.4	186.8	190.9	193.2	198.6	204.1	211.8	221.0	228.2	231.9	237.4
50°	170.4	171.8	174.5	179.5	183.1	189.1	195.9	203.6	212.8	217.8	221.0
52.5°	155.8	158.5	160.8	164.9	169.5	175.4	181.8	189.1	196.8	201.8	205.5
55°	141.2	143.5	146.2	148.5	154.0	159.5	166.7	173.6	180.4	185.0	189.1
57.5°	124.8	128.0	130.8	135.3	139.4	144.0	152.2	157.6	165.8	169.0	172.7
60°	110.7	113.9	116.2	119.8	123.5	129.4	134.9	141.7	148.5	152.6	157.2
62.5°	98.9	100.2	101.6	105.2	108.9	114.4	119.8	126.7	133.9	136.2	139.9
65°	87.0	88.4	90.7	93.8	96.6	99.8	105.7	111.2	118.0	121.6	123.0
67.5°	77.0	78.4	78.8	81.1	83.4	87.0	90.2	95.7	102.0	104.3	107.1
70°	65.6	67.9	68.3	70.2	71.1	73.3	77.0	81.1	86.1	90.2	92.5
72.5°	52.4	55.6	56.5	59.2	60.6	62.9	65.6	68.8	72.0	73.8	75.6
75°	42.8	43.7	44.2	46.5	48.7	51.9	53.3	55.1	57.9	60.1	62.0
77.5°	35.5	36.0	36.4	36.4	36.9	38.7	41.5	43.7	45.6	46.5	47.8
80°	28.7	28.2	28.2	28.7	28.7	28.7	29.6	32.8	33.7	36.0	35.5
82.5°	22.3	21.4	21.9	21.4	21.4	21.4	21.4	21.9	21.9	23.2	24.1
85°	14.6	15.0	14.6	14.6	14.1	14.6	14.1	14.1	13.7	13.7	13.2
87.5°	7.7	8.2	7.7	7.7	7.3	7.7	7.3	7.3	6.8	6.8	5.9
90°	20.7	19.9	19.2	18.4	19.2	16.9	14.6	12.3	10.0	9.2	8.4
92.5°	51.4	59.1	75.9	106.6	142.7	158.0	118.1	77.5	52.9	46.0	39.1
95°	146.5	187.1	276.1	368.9	454.8	404.9	279.2	164.9	99.7	84.8	69.8
97.5°	377.3	478.6	634.3	723.2	699.5	522.3	310.6	177.9	113.5	97.0	80.5
100°	752.4	842.1	904.2	877.4	726.3	490.8	289.1	175.6	121.9	107.0	92.0
102.5°	964.0	1007.0	994.0	885.1	676.4	444.8	270.7	178.7	131.9	118.5	105.1
105°	1088.3	1073.7	997.0	836.7	616.6	408.8	263.8	184.8	143.4	131.5	119.6
107.5°	1131.2	1071.4	951.0	767.7	563.7	382.7	262.3	194.8	158.0	146.8	135.7
110°	1116.7	1020.0	878.9	703.3	520.0	368.9	266.1	207.8	173.3	162.6	151.9

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1063.8	952.5	807.6	647.3	490.8	361.2	273.8	220.9	189.4	179.0	168.7
115°	992.4	879.7	746.2	604.4	471.7	360.5	282.2	235.5	206.3	196.0	185.6
117.5°	920.3	816.8	698.7	576.0	458.6	361.2	293.0	250.8	221.6	212.0	202.5
120°	858.2	766.2	662.6	554.5	450.2	364.3	305.2	265.4	237.8	228.2	218.6
122.5°	809.1	725.5	634.3	536.9	444.8	369.7	316.7	280.7	253.9	243.6	233.2
125°	766.9	693.3	609.7	522.3	440.2	375.0	329.0	295.3	268.4	258.0	247.7
127.5°	730.9	663.4	587.5	508.5	437.9	381.2	339.0	308.3	282.2	271.8	261.5
130°	697.9	635.8	566.8	497.7	435.6	387.3	349.0	319.8	294.5	284.2	273.8
132.5°	666.5	609.7	547.6	487.8	434.9	391.9	358.2	329.8	305.2	295.2	285.3
135°	635.0	585.2	530.7	479.3	434.1	396.5	365.8	339.8	316.0	305.6	295.3
137.5°	605.1	560.6	514.6	471.7	432.6	399.6	372.0	346.7	323.7	314.1	304.5
140°	576.7	539.9	500.8	464.8	431.8	402.6	376.6	353.6	331.3	321.7	312.1
142.5°	550.7	520.0	487.8	458.6	430.3	404.9	381.2	358.9	337.5	328.6	319.8
145°	527.7	503.1	477.8	453.3	428.7	405.7	384.2	363.5	343.6	334.8	326.0
147.5°	510.8	490.1	469.4	447.9	426.4	405.7	386.5	367.4	349.0	341.3	333.6
150°	493.9	477.8	460.2	442.5	423.4	405.7	387.3	371.2	353.6	346.7	339.8
152.5°	480.1	466.3	451.7	436.4	419.5	403.4	388.8	373.5	358.9	352.4	345.9
155°	467.1	455.6	443.3	430.3	414.9	401.9	388.8	376.6	363.5	358.2	352.8
157.5°	454.0	444.8	434.1	423.4	411.1	399.6	389.6	378.1	367.4	363.2	358.9
160°	442.5	434.9	426.4	416.5	406.5	398.0	389.6	380.4	371.2	367.4	363.5
162.5°	431.0	424.1	417.2	409.5	401.9	395.0	388.8	381.2	373.5	370.4	367.4
165°	419.5	414.1	409.5	403.4	397.3	391.9	387.3	381.9	375.8	373.1	370.4
167.5°	409.5	406.5	402.6	397.3	392.7	388.8	386.5	381.9	377.3	375.4	373.5
170°	401.1	398.0	395.7	391.9	388.1	385.8	384.2	381.2	377.3	376.6	375.8
172.5°	393.4	391.1	389.6	386.5	384.2	383.5	383.5	381.2	378.1	377.7	377.3
175°	386.5	385.0	384.2	382.7	381.2	381.2	381.9	380.4	378.9	378.5	378.1
177.5°	381.9	381.2	380.4	379.6	378.9	379.6	381.2	379.6	378.9	378.9	378.9
180°	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9	378.9

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	532.1	532.1	532.1	532.1
2.5°	518.4	521.6	528.0	533.5
5°	507.5	512.5	522.1	531.7
7.5°	494.3	502.0	514.3	527.6
10°	481.5	491.6	506.6	522.1
12.5°	468.8	479.3	495.2	515.3
15°	453.8	464.7	483.8	508.0
17.5°	440.5	455.1	472.4	496.6
20°	426.4	437.4	459.7	485.2
22.5°	408.7	426.9	447.8	474.7
25°	394.5	410.5	431.4	462.0
27.5°	377.2	395.9	421.4	448.3
30°	363.1	378.6	402.3	434.6
32.5°	346.7	364.9	389.5	421.4
35°	332.1	347.6	370.8	403.2
37.5°	314.8	331.7	357.6	386.3
40°	299.8	316.2	340.8	367.7
42.5°	281.5	298.9	323.5	346.2
45°	267.0	282.9	302.5	323.5
47.5°	249.2	266.1	285.2	299.8
50°	233.3	248.7	263.8	276.1
52.5°	215.9	230.1	243.7	252.8
55°	200.0	210.9	221.9	228.2
57.5°	181.3	191.8	200.9	204.6
60°	164.9	173.6	179.5	183.6
62.5°	147.6	154.0	158.5	160.8
65°	130.8	135.3	137.6	139.9
67.5°	113.4	117.5	118.9	121.6
70°	95.2	99.8	100.7	102.0
72.5°	81.5	81.5	83.4	85.2
75°	65.1	66.1	67.0	67.0
77.5°	51.0	51.0	51.9	52.4
80°	37.4	37.8	37.8	37.4
82.5°	25.5	26.4	25.5	25.1
85°	14.1	15.9	15.0	15.0
87.5°	5.9	5.9	6.8	5.9
90°	6.9	4.6	3.1	1.5
92.5°	31.4	24.5	16.9	11.5
95°	49.9	36.8	28.4	26.1
97.5°	60.6	49.1	42.2	41.4
100°	73.6	62.9	57.5	56.8
102.5°	89.0	79.0	74.4	72.9
105°	105.1	95.9	91.3	89.0
107.5°	121.9	112.7	108.1	105.8
110°	138.8	130.4	126.5	124.2

TEST NUMBER: P1012537

CATALOG NUMBER: S123RDIP-B340D805UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	155.7	147.3	143.4	141.1
115°	172.6	164.9	160.3	157.2
117.5°	187.9	181.0	177.2	173.3
120°	204.0	196.3	192.5	190.2
122.5°	219.3	210.9	207.1	204.8
125°	233.2	224.7	220.1	218.6
127.5°	245.4	237.0	231.6	229.3
130°	257.7	248.5	241.6	239.3
132.5°	269.2	257.7	250.0	247.0
135°	279.2	267.7	259.2	256.2
137.5°	288.4	276.1	267.7	264.6
140°	296.8	284.5	276.9	273.0
142.5°	304.5	293.7	285.3	282.2
145°	312.9	301.4	294.5	292.2
147.5°	320.6	310.6	303.7	302.2
150°	329.0	319.0	312.9	312.1
152.5°	336.7	328.3	322.1	322.1
155°	344.4	336.7	332.1	332.1
157.5°	351.3	344.4	340.5	339.8
160°	358.2	352.0	349.0	349.0
162.5°	362.8	358.2	355.9	355.9
165°	367.4	363.5	362.0	362.8
167.5°	371.2	368.1	367.4	368.1
170°	374.3	372.0	371.2	372.7
172.5°	376.6	375.0	375.0	375.8
175°	378.1	376.6	377.3	378.1
177.5°	378.9	378.1	378.9	379.6
180°	378.9	378.9	378.9	378.9

(END OF REPORT)