

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012542

Luminaire Tested: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012542
REPORT IS A COMBINATION OF REPORTS P993309 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D805UB40-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4135.0 lumens
Efficiency: N/A
Efficacy: 121.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	30	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	28	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	25	24	22
5	66	55	47	42	59	50	43	38	40	36	32	31	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	28	25	22	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14
9	49	37	30	25	44	34	27	23	28	23	20	22	18	16	16	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5672	5672	5672	5672
5°	5675	6532	5690	4846
10°	5626	7885	5650	4233
15°	5568	8949	5568	3732
20°	5453	9653	5484	3311
25°	5370	9171	5359	3021
30°	5273	6354	5262	2737
35°	5155	4079	5132	2524
40°	5010	2880	4985	2311
45°	4757	2305	4749	2104
50°	4446	1929	4431	1862
55°	4095	1590	4062	1579
60°	3751	1314	3714	1343
65°	3348	1052	3370	1138
70°	2974	730	3057	921
75°	2522	542	2625	707
80°	2009	358	2177	531
85°	1431	171	1556	330

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7571 cd/sqm

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.7	1.3
10°-20°	162.0	3.9
20°-30°	255.1	6.2
30°-40°	265.3	6.4
40°-50°	226.9	5.5
50°-60°	173.0	4.2
60°-70°	110.9	2.7
70°-80°	53.1	1.3
80°-90°	16.0	0.4
90°-100°	203.5	4.9
100°-110°	595.8	14.4
110°-120°	581.8	14.1
120°-130°	463.4	11.2
130°-140°	365.6	8.8
140°-150°	272.7	6.6
150°-160°	190.1	4.6
160°-170°	111.7	2.7
170°-180°	36.3	0.9
0°-30°	468.8	11.3
0°-40°	734.1	17.8
0°-60°	1134.1	27.4
0°-90°	1314.1	31.8
90°-120°	1381.1	33.4
90°-150°	2482.7	60.0
90°-180°	2821.0	68.2
0°-180°	4135.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	526	626	528	464	526	50
15°	503	889	503	371	503	141
25°	457	916	456	302	457	211
35°	399	397	397	246	399	250
45°	320	212	320	194	320	247
55°	226	133	224	132	226	203
65°	138	77	139	83	138	138
75°	66	32	69	42	66	72
85°	15	8	16	15	15	17
90°	2	22	2	22	2	3
95°	26	88	26	88	26	27
105°	88	966	88	966	88	94
115°	156	1174	156	1174	156	154
125°	216	926	216	926	216	192
135°	254	751	254	751	254	196
145°	289	587	289	587	289	181
155°	329	487	329	487	329	151
165°	359	424	359	424	359	101
175°	374	382	374	382	374	36
180°	375	375	375	375	375	

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	528.2	531.9	534.6	536.4	540.9	543.6	545.8	549.9	549.9	550.8	552.6
5°	526.4	534.1	539.5	546.7	556.2	560.7	567.0	572.5	580.1	584.2	588.2
7.5°	522.4	533.2	544.5	555.3	569.3	578.3	584.6	598.6	608.5	620.7	630.2
10°	517.0	531.9	546.3	563.0	581.9	595.5	604.9	623.4	642.4	659.5	674.0
12.5°	510.2	528.2	549.0	569.3	595.9	609.4	624.8	647.8	674.9	696.5	715.9
15°	503.0	523.7	547.2	572.0	605.4	624.3	646.4	674.4	704.6	735.8	762.4
17.5°	491.7	517.9	544.0	580.1	619.4	630.7	649.6	687.9	725.4	753.4	785.8
20°	480.4	509.8	542.7	575.2	617.6	643.7	661.3	701.9	742.1	775.9	807.0
22.5°	470.1	500.7	535.0	576.1	615.8	641.9	664.0	706.4	752.9	790.8	829.1
25°	457.4	490.8	528.7	567.5	615.8	635.6	660.0	709.1	758.3	802.1	849.4
27.5°	443.9	477.7	515.2	554.9	599.1	628.4	652.3	705.1	765.1	812.0	860.7
30°	430.4	465.1	501.2	536.8	586.4	614.4	641.9	700.1	768.7	822.4	859.8
32.5°	417.3	446.6	482.2	517.0	566.1	596.8	627.9	695.2	770.0	815.2	833.2
35°	399.2	429.9	458.8	495.8	545.4	575.6	612.2	694.7	764.2	792.1	783.1
37.5°	382.5	408.3	435.8	468.7	519.7	558.9	596.8	683.0	744.8	746.6	695.6
40°	364.0	385.2	408.3	443.0	498.0	536.8	577.9	664.9	709.6	683.0	593.2
42.5°	342.8	361.8	379.8	413.7	473.7	517.0	561.2	642.4	658.6	597.3	503.9
45°	320.3	335.6	352.3	388.0	448.0	490.8	535.0	607.6	591.0	504.3	415.5
47.5°	296.8	309.9	326.2	358.6	420.4	464.2	506.1	558.0	515.6	422.7	348.3
50°	273.4	283.7	299.5	332.9	392.5	432.2	471.0	504.8	445.2	362.7	287.8
52.5°	250.4	258.5	274.7	303.1	360.9	398.8	426.7	439.8	379.4	299.5	249.9
55°	226.0	235.0	245.9	274.7	332.0	360.0	378.5	378.0	315.8	254.0	206.6
57.5°	202.5	210.7	220.1	249.0	295.5	314.4	330.2	322.5	263.4	208.0	177.3
60°	181.8	186.3	196.7	221.0	256.2	272.5	281.5	268.4	215.2	175.5	146.6
62.5°	159.2	163.8	172.3	195.3	217.0	225.6	233.2	216.5	177.7	143.0	125.4
65°	138.5	144.4	149.8	168.3	180.0	190.4	189.5	175.5	138.9	116.4	102.0
67.5°	120.4	122.7	127.2	138.5	143.9	151.6	152.0	136.2	111.9	94.7	86.2
70°	101.0	103.3	106.5	111.9	115.5	117.3	116.4	102.4	84.4	74.0	66.3
72.5°	84.4	83.9	86.2	86.2	89.8	89.3	86.6	75.8	64.1	55.5	51.0
75°	66.3	66.8	67.2	66.3	65.0	63.2	60.9	52.8	45.1	41.1	37.0
77.5°	51.9	51.0	51.4	48.3	46.5	44.7	41.5	37.4	31.1	30.2	28.4
80°	37.0	36.5	36.1	34.7	30.7	28.9	26.6	24.4	23.0	22.1	21.7
82.5°	24.8	24.8	23.9	21.2	18.9	17.6	17.1	16.2	14.9	14.9	14.4
85°	14.9	14.4	13.5	10.8	9.5	9.5	9.5	9.5	8.6	8.6	8.1
87.5°	5.9	5.4	4.1	4.1	3.6	3.6	3.6	3.2	3.2	2.7	2.7
90°	1.5	3.0	4.6	6.8	8.4	9.2	9.9	12.1	14.4	16.7	19.0
92.5°	11.4	16.7	24.3	31.1	38.7	45.6	52.4	76.7	116.9	156.4	141.2
95°	25.8	28.1	36.4	49.3	69.1	83.9	98.7	163.2	276.3	400.8	450.2
97.5°	41.0	41.8	48.6	60.0	79.7	96.1	112.4	176.1	307.5	517.0	692.3
100°	56.2	56.9	62.2	72.9	91.1	105.9	120.7	173.8	286.2	485.9	718.9
102.5°	72.1	73.6	78.2	88.1	104.0	117.3	130.6	176.9	268.0	440.3	669.6
105°	88.1	90.3	94.9	104.0	118.4	130.2	142.0	183.0	261.1	404.6	610.4
107.5°	104.8	107.0	111.6	120.7	134.4	145.4	156.4	192.8	259.6	378.8	558.0
110°	123.0	125.3	129.1	137.4	150.3	161.0	171.6	205.7	263.4	365.1	514.7

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	139.7	142.0	145.8	154.1	167.0	177.2	187.5	218.6	271.0	357.6	485.9
115°	155.6	158.7	163.2	170.8	183.7	194.0	204.2	233.1	279.4	356.8	466.9
117.5°	171.6	175.4	179.2	186.0	200.4	209.9	219.4	248.2	290.0	357.6	454.0
120°	188.3	190.5	194.3	201.9	216.4	225.8	235.3	262.7	302.1	360.6	445.6
122.5°	202.7	205.0	208.8	217.1	230.8	241.0	251.3	277.8	313.5	365.9	440.3
125°	216.4	217.9	222.4	230.8	245.2	255.4	265.7	292.3	325.7	371.2	435.7
127.5°	227.0	229.3	234.6	242.9	258.9	269.2	279.4	305.2	335.5	377.3	433.5
130°	236.9	239.1	246.0	255.1	271.0	281.2	291.5	316.6	345.4	383.4	431.2
132.5°	244.4	247.5	255.1	266.5	282.4	292.2	302.1	326.4	354.5	387.9	430.4
135°	253.6	256.6	264.9	276.3	292.3	302.6	312.8	336.3	362.1	392.5	429.7
137.5°	261.9	264.9	273.3	285.4	301.4	310.9	320.4	343.1	368.2	395.5	428.2
140°	270.3	274.1	281.6	293.8	309.0	318.5	328.0	350.0	372.7	398.6	427.4
142.5°	279.4	282.4	290.8	301.4	316.6	325.3	334.0	355.3	377.3	400.8	425.9
145°	289.2	291.5	298.3	309.7	322.6	331.4	340.1	359.8	380.3	401.6	424.4
147.5°	299.1	300.6	307.5	317.3	330.2	337.8	345.4	363.6	382.6	401.6	422.1
150°	309.0	309.7	315.8	325.7	336.3	343.2	350.0	367.4	383.4	401.6	419.0
152.5°	318.8	318.8	324.9	333.3	342.4	348.8	355.3	369.7	384.9	399.3	415.3
155°	328.7	328.7	333.3	340.9	349.2	354.5	359.8	372.7	384.9	397.8	410.7
157.5°	336.3	337.1	340.9	347.7	355.3	359.5	363.6	374.3	385.6	395.5	406.9
160°	345.4	345.4	348.4	354.5	359.8	363.6	367.4	376.5	385.6	394.0	402.3
162.5°	352.2	352.2	354.5	359.1	363.6	366.6	369.7	377.3	384.9	391.0	397.8
165°	359.1	358.3	359.8	363.6	366.7	369.4	372.0	378.1	383.4	387.9	393.2
167.5°	364.4	363.6	364.4	367.4	369.7	371.6	373.5	378.1	382.6	384.9	388.7
170°	368.9	367.4	368.2	370.5	372.0	372.8	373.5	377.3	380.3	381.9	384.1
172.5°	372.0	371.2	371.2	372.7	373.5	373.9	374.3	377.3	379.6	379.6	380.3
175°	374.3	373.5	372.7	374.3	374.3	374.6	375.0	376.5	378.1	377.3	377.3
177.5°	375.8	375.0	374.3	375.0	375.0	375.0	375.0	375.8	377.3	375.8	375.0
180°	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	556.2	556.2	560.3	564.3	562.1	563.4	568.4	566.6	570.2	569.8	571.1
5°	598.2	603.1	607.2	615.8	617.1	615.8	624.3	626.6	630.7	625.7	627.9
7.5°	645.5	655.9	665.8	678.5	682.5	683.4	687.9	694.3	699.7	689.7	694.7
10°	691.6	707.3	727.6	738.9	748.8	752.5	756.1	760.1	766.4	772.3	767.8
12.5°	741.2	764.2	783.6	803.9	816.1	814.7	825.1	827.8	832.7	834.1	835.9
15°	781.8	814.3	826.4	856.7	859.4	868.4	880.1	890.5	891.8	889.1	889.1
17.5°	820.6	848.5	870.2	894.6	899.5	907.2	922.1	927.0	928.8	928.4	928.4
20°	852.1	870.6	907.2	927.5	935.6	945.5	955.9	962.2	963.6	965.4	962.7
22.5°	872.9	900.9	930.6	947.3	954.1	957.7	964.5	966.3	964.0	964.5	964.9
25°	889.1	916.7	934.7	939.2	938.8	934.2	929.3	920.7	919.8	916.2	909.0
27.5°	893.6	904.0	901.8	883.3	864.8	863.0	833.2	817.0	798.5	801.2	790.8
30°	869.3	855.8	823.7	776.8	757.4	725.8	692.5	657.7	644.2	629.3	656.8
32.5°	809.7	761.5	704.6	643.7	611.3	583.3	547.6	522.4	507.9	495.8	519.2
35°	720.0	644.6	569.3	511.6	484.9	459.7	426.3	413.7	395.6	397.4	399.7
37.5°	604.5	521.5	464.6	407.8	390.2	379.8	355.5	336.1	329.8	328.0	328.0
40°	496.2	428.1	377.6	332.9	319.4	310.8	291.4	282.4	275.6	273.8	276.1
42.5°	410.5	352.3	313.1	283.3	273.8	263.0	254.9	243.6	242.2	239.1	243.1
45°	344.6	294.1	264.8	243.1	235.0	231.0	221.9	215.2	212.5	212.0	215.2
47.5°	292.3	253.1	227.4	213.8	207.5	203.5	195.8	193.1	190.4	191.3	189.9
50°	245.4	216.1	199.4	187.2	183.2	179.1	174.1	171.4	170.1	170.1	169.6
52.5°	210.7	186.3	175.5	164.2	162.4	160.1	154.7	152.9	150.7	150.2	152.0
55°	180.4	163.8	152.9	146.2	144.4	139.8	137.6	135.3	134.0	133.1	133.5
57.5°	154.3	141.6	134.4	128.6	125.4	123.6	119.5	119.1	118.2	118.2	117.7
60°	132.6	123.6	115.0	111.4	109.2	106.9	106.5	103.8	102.4	103.3	102.9
62.5°	112.3	105.1	100.1	96.1	94.7	92.9	91.6	90.7	89.3	89.8	89.8
65°	93.8	88.0	84.4	80.7	80.3	78.5	78.0	77.1	77.1	76.7	77.6
67.5°	77.1	73.1	69.9	67.7	66.3	66.8	65.0	63.6	63.6	63.2	64.5
70°	61.4	59.1	55.9	53.2	51.4	51.4	49.2	48.7	48.7	48.7	48.3
72.5°	47.4	43.3	42.0	41.1	41.1	41.1	40.1	40.1	39.7	40.1	39.7
75°	35.2	34.7	33.8	33.4	33.4	32.9	32.5	32.5	32.5	32.5	32.5
77.5°	27.5	27.5	26.6	26.2	26.2	26.2	25.7	25.7	25.3	25.3	25.3
80°	20.3	20.3	19.4	19.4	19.4	18.9	18.9	18.9	19.4	18.9	18.9
82.5°	14.0	14.0	13.5	14.0	13.5	13.1	13.1	13.1	12.6	13.1	13.1
85°	8.1	8.1	7.7	7.2	7.7	7.7	7.2	7.7	7.2	7.7	7.2
87.5°	3.2	2.7	2.7	2.7	2.3	2.7	2.3	2.3	2.7	2.3	2.7
90°	18.2	19.0	19.7	20.5	21.2	22.0	21.3	22.0	22.8	22.0	22.8
92.5°	105.5	75.2	58.5	50.9	48.2	45.5	44.0	41.0	41.8	40.2	41.8
95°	365.1	273.3	185.2	145.0	131.4	117.7	103.2	96.4	91.1	88.1	91.1
97.5°	715.9	627.8	473.7	373.5	330.2	287.0	236.1	207.2	189.0	180.7	189.0
100°	868.5	895.0	833.5	744.7	690.8	636.9	560.2	504.8	475.2	476.0	475.2
102.5°	876.1	983.9	996.8	954.2	925.0	895.8	840.4	799.4	775.8	753.8	775.8
105°	828.2	986.9	1062.8	1077.2	1067.4	1057.5	1022.6	993.7	969.4	965.6	969.4
107.5°	759.9	941.3	1060.5	1119.7	1130.0	1140.2	1135.7	1122.0	1112.1	1103.8	1112.1
110°	696.1	870.0	1009.7	1105.3	1131.9	1158.5	1179.7	1185.8	1184.3	1182.7	1184.3

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	640.7	799.4	942.9	1052.9	1089.0	1125.1	1168.3	1190.3	1197.9	1198.7	1197.9
115°	598.2	738.6	870.7	982.3	1023.7	1065.1	1122.0	1155.4	1170.6	1174.4	1170.6
117.5°	570.1	691.6	808.5	911.0	953.9	996.8	1056.0	1093.2	1115.9	1121.3	1115.9
120°	548.9	655.9	758.4	849.5	887.8	926.2	986.1	1028.6	1046.9	1051.4	1046.9
122.5°	531.4	627.8	718.2	800.9	835.8	870.7	922.4	959.6	980.1	986.1	980.1
125°	517.0	603.5	686.3	759.1	789.5	819.9	868.5	901.9	920.8	926.2	920.8
127.5°	503.3	581.5	656.7	723.5	751.6	779.6	823.7	852.5	870.0	874.5	870.0
130°	492.7	561.0	629.3	690.8	716.6	742.4	782.7	810.0	826.0	832.0	826.0
132.5°	482.8	542.0	603.5	659.7	684.0	708.3	745.5	772.8	786.5	790.3	786.5
135°	474.5	525.3	579.2	628.6	650.2	671.8	709.0	731.8	745.5	750.8	745.5
137.5°	466.9	509.4	554.9	599.0	618.4	637.7	669.6	693.1	704.5	709.0	704.5
140°	460.0	495.7	534.4	570.9	587.2	603.5	632.4	653.6	665.8	665.0	665.8
142.5°	454.0	482.8	514.7	545.1	558.8	572.4	595.9	614.1	624.8	624.0	624.8
145°	448.7	472.9	498.0	522.3	533.3	544.3	563.3	579.2	585.3	586.8	585.3
147.5°	443.3	464.6	485.1	505.6	513.6	521.5	536.7	548.1	554.2	554.9	554.2
150°	438.0	455.5	472.9	488.9	496.1	503.3	514.7	523.1	527.6	527.6	527.6
152.5°	432.0	447.1	461.6	475.2	480.9	486.6	495.0	502.6	504.8	504.8	504.8
155°	425.9	438.8	450.9	462.3	466.8	471.4	478.3	484.3	485.9	486.6	485.9
157.5°	419.0	429.7	440.3	449.4	453.2	457.0	463.1	467.6	469.2	469.2	469.2
160°	412.2	422.1	430.4	438.0	440.6	443.3	448.7	453.2	453.2	452.5	453.2
162.5°	405.4	413.0	419.8	426.6	428.9	431.2	434.2	438.0	438.0	437.3	438.0
165°	399.3	405.4	409.9	415.3	417.2	419.0	422.1	425.1	424.4	424.4	424.4
167.5°	393.2	398.6	402.3	405.4	406.9	408.4	409.9	412.2	411.5	411.5	411.5
170°	387.9	391.7	394.0	397.0	397.8	398.6	399.3	400.8	400.1	400.1	400.1
172.5°	382.6	385.6	387.2	389.4	389.8	390.2	390.2	391.7	390.2	389.4	390.2
175°	378.8	380.3	381.1	382.6	382.6	382.6	382.6	383.4	382.6	381.9	382.6
177.5°	375.8	376.5	377.3	378.1	378.1	378.1	377.3	378.1	376.5	376.5	376.5
180°	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	568.8	566.1	564.3	563.0	561.6	565.7	560.3	554.4	550.4	547.6	546.7
5°	628.4	622.5	617.6	613.5	614.4	614.4	604.9	594.6	585.5	580.6	575.2
7.5°	697.4	691.1	681.2	678.9	677.1	665.8	656.4	637.4	626.1	614.9	604.9
10°	766.0	757.9	748.4	745.2	740.7	726.7	712.3	687.9	674.0	653.2	640.1
12.5°	830.0	820.1	810.6	808.4	801.6	789.4	764.6	739.4	715.5	693.4	670.3
15°	883.7	881.0	866.6	857.6	842.7	826.0	820.6	786.3	756.1	733.1	691.6
17.5°	928.8	916.2	902.7	896.8	890.9	871.5	852.1	817.0	784.5	750.6	724.0
20°	964.9	950.9	941.5	932.9	930.2	908.1	877.4	846.3	810.6	772.8	738.0
22.5°	966.7	964.9	958.6	953.6	948.2	933.8	909.4	870.6	832.7	791.2	745.7
25°	929.3	926.6	944.6	940.1	943.7	938.3	925.2	892.7	848.5	799.8	753.8
27.5°	816.5	844.0	872.4	882.4	889.1	908.5	914.9	896.8	861.2	809.3	757.9
30°	663.1	699.7	745.7	770.5	789.4	825.5	872.4	878.3	861.6	820.1	757.0
32.5°	520.6	554.0	591.0	620.3	645.5	719.5	782.7	828.2	836.4	814.7	759.2
35°	419.5	434.0	469.2	497.1	531.4	594.6	669.0	742.5	792.1	794.9	752.5
37.5°	346.0	353.7	384.3	400.1	420.4	475.9	545.4	641.5	718.6	755.2	733.5
40°	286.5	304.0	321.6	330.7	345.1	383.4	450.2	525.5	621.2	688.8	704.2
42.5°	248.6	256.2	267.5	280.1	289.2	322.5	367.2	436.2	522.4	616.7	659.1
45°	219.2	221.9	233.7	241.8	251.3	274.7	306.3	364.0	439.8	532.8	604.9
47.5°	194.9	200.3	206.6	211.6	217.9	235.9	263.0	305.0	371.7	454.7	532.3
50°	173.2	176.4	184.5	186.8	191.3	203.9	224.7	256.7	311.7	378.0	458.3
52.5°	152.9	158.8	161.9	165.1	169.2	179.5	193.1	219.2	260.7	323.0	391.1
55°	137.1	138.9	143.5	146.2	149.3	156.5	168.3	187.7	220.1	269.8	334.3
57.5°	121.8	121.8	126.3	128.6	131.7	137.1	147.5	162.4	185.9	222.8	281.9
60°	105.6	106.0	109.6	112.3	113.2	118.6	127.2	138.9	157.0	184.1	232.3
62.5°	91.1	93.4	95.2	96.1	99.2	102.4	109.6	117.7	130.4	154.3	188.6
65°	78.9	79.4	80.7	81.7	83.0	86.6	92.0	97.4	108.3	125.9	153.8
67.5°	65.0	66.8	68.6	68.6	69.9	71.7	77.1	81.7	89.8	100.1	119.1
70°	48.7	49.6	52.3	53.7	55.5	58.6	61.4	64.1	70.4	78.0	92.5
72.5°	40.6	40.6	41.5	42.0	42.0	44.2	48.3	51.0	54.1	59.5	69.5
75°	32.5	32.5	33.8	33.4	34.3	35.2	35.6	37.4	39.2	43.3	49.2
77.5°	25.7	26.2	26.2	26.6	26.6	27.1	27.5	28.4	29.3	31.6	34.3
80°	18.9	19.4	19.4	19.8	19.8	20.3	20.8	21.2	22.1	23.0	24.4
82.5°	13.1	13.5	13.5	14.0	13.5	14.0	14.4	14.4	14.9	15.8	16.2
85°	7.7	7.7	8.1	7.7	7.7	7.7	8.1	8.1	8.6	9.9	9.9
87.5°	2.3	2.7	2.3	2.7	2.7	2.7	2.7	3.2	3.2	3.6	4.1
90°	22.0	21.3	22.0	21.2	20.5	19.7	19.0	18.2	19.0	16.7	14.4
92.5°	41.0	44.0	45.5	48.2	50.9	58.5	75.2	105.5	141.2	156.4	116.9
95°	96.4	103.2	117.7	131.4	145.0	185.2	273.3	365.1	450.2	400.8	276.3
97.5°	207.2	236.1	287.0	330.2	373.5	473.7	627.8	715.9	692.3	517.0	307.5
100°	504.8	560.2	636.9	690.8	744.7	833.5	895.0	868.5	718.9	485.9	286.2
102.5°	799.4	840.4	895.8	925.0	954.2	996.8	983.9	876.1	669.6	440.3	268.0
105°	993.7	1022.6	1057.5	1067.4	1077.2	1062.8	986.9	828.2	610.4	404.6	261.1
107.5°	1122.0	1135.7	1140.2	1130.0	1119.7	1060.5	941.3	759.9	558.0	378.8	259.6
110°	1185.8	1179.7	1158.5	1131.9	1105.3	1009.7	870.0	696.1	514.7	365.1	263.4

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1190.3	1168.3	1125.1	1089.0	1052.9	942.9	799.4	640.7	485.9	357.6	271.0
115°	1155.4	1122.0	1065.1	1023.7	982.3	870.7	738.6	598.2	466.9	356.8	279.4
117.5°	1093.2	1056.0	996.8	953.9	911.0	808.5	691.6	570.1	454.0	357.6	290.0
120°	1028.6	986.1	926.2	887.8	849.5	758.4	655.9	548.9	445.6	360.6	302.1
122.5°	959.6	922.4	870.7	835.8	800.9	718.2	627.8	531.4	440.3	365.9	313.5
125°	901.9	868.5	819.9	789.5	759.1	686.3	603.5	517.0	435.7	371.2	325.7
127.5°	852.5	823.7	779.6	751.6	723.5	656.7	581.5	503.3	433.5	377.3	335.5
130°	810.0	782.7	742.4	716.6	690.8	629.3	561.0	492.7	431.2	383.4	345.4
132.5°	772.8	745.5	708.3	684.0	659.7	603.5	542.0	482.8	430.4	387.9	354.5
135°	731.8	709.0	671.8	650.2	628.6	579.2	525.3	474.5	429.7	392.5	362.1
137.5°	693.1	669.6	637.7	618.4	599.0	554.9	509.4	466.9	428.2	395.5	368.2
140°	653.6	632.4	603.5	587.2	570.9	534.4	495.7	460.0	427.4	398.6	372.7
142.5°	614.1	595.9	572.4	558.8	545.1	514.7	482.8	454.0	425.9	400.8	377.3
145°	579.2	563.3	544.3	533.3	522.3	498.0	472.9	448.7	424.4	401.6	380.3
147.5°	548.1	536.7	521.5	513.6	505.6	485.1	464.6	443.3	422.1	401.6	382.6
150°	523.1	514.7	503.3	496.1	488.9	472.9	455.5	438.0	419.0	401.6	383.4
152.5°	502.6	495.0	486.6	480.9	475.2	461.6	447.1	432.0	415.3	399.3	384.9
155°	484.3	478.3	471.4	466.8	462.3	450.9	438.8	425.9	410.7	397.8	384.9
157.5°	467.6	463.1	457.0	453.2	449.4	440.3	429.7	419.0	406.9	395.5	385.6
160°	453.2	448.7	443.3	440.6	438.0	430.4	422.1	412.2	402.3	394.0	385.6
162.5°	438.0	434.2	431.2	428.9	426.6	419.8	413.0	405.4	397.8	391.0	384.9
165°	425.1	422.1	419.0	417.2	415.3	409.9	405.4	399.3	393.2	387.9	383.4
167.5°	412.2	409.9	408.4	406.9	405.4	402.3	398.6	393.2	388.7	384.9	382.6
170°	400.8	399.3	398.6	397.8	397.0	394.0	391.7	387.9	384.1	381.9	380.3
172.5°	391.7	390.2	390.2	389.8	389.4	387.2	385.6	382.6	380.3	379.6	379.6
175°	383.4	382.6	382.6	382.6	382.6	381.1	380.3	378.8	377.3	377.3	378.1
177.5°	378.1	377.3	378.1	378.1	378.1	377.3	376.5	375.8	375.0	375.8	377.3
180°	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	545.4	543.1	540.9	540.9	535.9	531.4	529.2	530.1	527.3	523.7	520.1
5°	569.3	560.3	558.5	553.5	546.7	537.3	532.3	527.8	522.4	515.2	508.4
7.5°	591.4	579.7	573.4	568.4	555.3	542.2	531.4	524.2	514.7	503.9	495.8
10°	620.3	598.6	591.9	580.6	562.1	543.6	531.0	519.2	506.1	493.5	482.7
12.5°	643.3	618.5	605.8	594.6	570.7	547.2	526.0	511.6	495.8	481.8	467.8
15°	669.4	641.5	619.4	605.8	575.6	547.2	523.3	503.0	485.4	468.3	456.1
17.5°	682.1	646.9	637.0	617.6	573.8	545.4	516.1	494.4	473.2	453.4	438.9
20°	701.9	660.9	636.1	623.0	584.2	542.2	507.9	483.1	461.0	439.8	424.5
22.5°	703.3	658.6	642.4	617.6	569.8	532.8	500.7	470.5	444.8	424.9	409.2
25°	700.1	654.6	632.0	612.2	572.5	527.3	486.3	456.5	431.3	408.3	389.8
27.5°	698.8	642.8	621.6	601.8	557.1	511.6	477.7	443.9	415.0	394.7	375.8
30°	697.0	630.2	604.5	581.5	540.4	499.4	458.8	429.5	401.9	376.2	357.3
32.5°	685.2	613.1	586.9	562.5	518.3	477.3	445.2	414.1	384.3	360.4	343.3
35°	681.6	597.3	563.0	536.8	493.5	457.0	423.1	397.4	369.5	345.5	325.2
37.5°	671.3	581.0	544.0	510.7	465.5	430.8	406.0	380.3	353.2	327.5	311.3
40°	653.2	562.1	520.1	485.8	439.4	404.2	381.2	362.2	335.6	312.6	292.8
42.5°	626.6	542.7	497.6	461.5	410.1	377.1	358.2	340.1	317.6	293.7	277.4
45°	595.9	517.0	475.0	434.9	382.5	350.5	330.7	319.8	299.1	278.8	259.8
47.5°	554.0	490.4	448.9	407.4	354.1	323.0	307.2	296.4	281.9	259.8	244.5
50°	501.2	456.1	416.8	379.8	326.2	296.4	280.6	272.5	260.3	244.5	229.6
52.5°	442.5	416.4	383.9	349.6	297.7	269.8	255.3	249.0	240.0	225.1	212.5
55°	383.4	372.2	350.1	316.2	268.0	245.0	232.3	224.2	217.4	206.6	195.8
57.5°	330.7	325.2	309.9	283.7	243.1	219.2	208.4	203.0	197.6	189.5	178.6
60°	276.1	281.9	266.2	253.1	216.1	195.3	185.9	180.0	177.3	170.1	163.3
62.5°	228.7	234.1	225.1	215.2	189.0	170.5	164.7	159.2	157.4	151.1	144.4
65°	185.9	192.6	185.9	180.4	164.7	149.3	142.1	139.4	137.6	133.5	128.1
67.5°	148.0	154.7	151.6	144.8	139.8	127.2	123.2	120.4	119.5	116.4	111.9
70°	111.4	120.9	121.8	117.7	113.2	107.4	104.7	103.8	101.5	98.8	96.1
72.5°	80.3	91.1	91.6	91.6	88.9	88.9	86.2	84.8	84.8	82.1	78.9
75°	59.1	66.3	67.2	68.1	69.5	70.8	69.0	69.0	68.6	65.9	64.5
77.5°	39.2	45.6	47.8	51.0	52.8	52.8	53.7	54.6	53.7	52.3	51.4
80°	25.3	29.8	32.5	34.3	37.0	38.3	39.7	40.1	39.2	38.8	37.4
82.5°	16.7	18.0	19.4	21.7	24.8	27.1	27.1	26.6	27.5	27.1	26.6
85°	9.5	10.4	10.8	11.3	13.1	15.3	15.8	16.2	17.1	16.2	15.3
87.5°	3.6	4.1	4.1	4.1	5.0	5.4	6.8	8.6	8.1	7.2	7.2
90°	12.1	9.9	9.2	8.4	6.8	4.6	3.0	1.5	3.0	4.6	6.8
92.5°	76.7	52.4	45.6	38.7	31.1	24.3	16.7	11.4	16.7	24.3	31.1
95°	163.2	98.7	83.9	69.1	49.3	36.4	28.1	25.8	28.1	36.4	49.3
97.5°	176.1	112.4	96.1	79.7	60.0	48.6	41.8	41.0	41.8	48.6	60.0
100°	173.8	120.7	105.9	91.1	72.9	62.2	56.9	56.2	56.9	62.2	72.9
102.5°	176.9	130.6	117.3	104.0	88.1	78.2	73.6	72.1	73.6	78.2	88.1
105°	183.0	142.0	130.2	118.4	104.0	94.9	90.3	88.1	90.3	94.9	104.0
107.5°	192.8	156.4	145.4	134.4	120.7	111.6	107.0	104.8	107.0	111.6	120.7
110°	205.7	171.6	161.0	150.3	137.4	129.1	125.3	123.0	125.3	129.1	137.4

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	218.6	187.5	177.2	167.0	154.1	145.8	142.0	139.7	142.0	145.8	154.1
115°	233.1	204.2	194.0	183.7	170.8	163.2	158.7	155.6	158.7	163.2	170.8
117.5°	248.2	219.4	209.9	200.4	186.0	179.2	175.4	171.6	175.4	179.2	186.0
120°	262.7	235.3	225.8	216.4	201.9	194.3	190.5	188.3	190.5	194.3	201.9
122.5°	277.8	251.3	241.0	230.8	217.1	208.8	205.0	202.7	205.0	208.8	217.1
125°	292.3	265.7	255.4	245.2	230.8	222.4	217.9	216.4	217.9	222.4	230.8
127.5°	305.2	279.4	269.2	258.9	242.9	234.6	229.3	227.0	229.3	234.6	242.9
130°	316.6	291.5	281.2	271.0	255.1	246.0	239.1	236.9	239.1	246.0	255.1
132.5°	326.4	302.1	292.2	282.4	266.5	255.1	247.5	244.4	247.5	255.1	266.5
135°	336.3	312.8	302.6	292.3	276.3	264.9	256.6	253.6	256.6	264.9	276.3
137.5°	343.1	320.4	310.9	301.4	285.4	273.3	264.9	261.9	264.9	273.3	285.4
140°	350.0	328.0	318.5	309.0	293.8	281.6	274.1	270.3	274.1	281.6	293.8
142.5°	355.3	334.0	325.3	316.6	301.4	290.8	282.4	279.4	282.4	290.8	301.4
145°	359.8	340.1	331.4	322.6	309.7	298.3	291.5	289.2	291.5	298.3	309.7
147.5°	363.6	345.4	337.8	330.2	317.3	307.5	300.6	299.1	300.6	307.5	317.3
150°	367.4	350.0	343.2	336.3	325.7	315.8	309.7	309.0	309.7	315.8	325.7
152.5°	369.7	355.3	348.8	342.4	333.3	324.9	318.8	318.8	318.8	324.9	333.3
155°	372.7	359.8	354.5	349.2	340.9	333.3	328.7	328.7	328.7	333.3	340.9
157.5°	374.3	363.6	359.5	355.3	347.7	340.9	337.1	336.3	337.1	340.9	347.7
160°	376.5	367.4	363.6	359.8	354.5	348.4	345.4	345.4	345.4	348.4	354.5
162.5°	377.3	369.7	366.6	363.6	359.1	354.5	352.2	352.2	352.2	354.5	359.1
165°	378.1	372.0	369.4	366.7	363.6	359.8	358.3	359.1	358.3	359.8	363.6
167.5°	378.1	373.5	371.6	369.7	367.4	364.4	363.6	364.4	363.6	364.4	367.4
170°	377.3	373.5	372.8	372.0	370.5	368.2	367.4	368.9	367.4	368.2	370.5
172.5°	377.3	374.3	373.9	373.5	372.7	371.2	371.2	372.0	371.2	371.2	372.7
175°	376.5	375.0	374.6	374.3	374.3	372.7	373.5	374.3	373.5	372.7	374.3
177.5°	375.8	375.0	375.0	375.0	375.0	374.3	375.0	375.8	375.0	374.3	375.0
180°	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	520.1	517.9	517.0	514.7	509.3	505.7	501.6	498.9	499.4	497.1	498.5
5°	503.9	503.4	500.3	495.8	488.1	484.0	476.8	473.2	471.4	471.9	469.2
7.5°	490.4	486.3	484.0	476.8	469.6	461.0	455.2	452.0	449.3	446.6	444.8
10°	475.0	471.4	467.8	460.1	450.2	442.1	434.0	430.8	426.7	424.9	423.6
12.5°	458.8	456.5	452.0	443.0	431.7	424.0	414.6	412.8	407.4	403.7	402.8
15°	443.9	442.5	434.4	424.0	412.8	405.1	397.0	391.6	382.5	384.3	381.2
17.5°	428.1	422.2	417.3	403.3	397.9	386.1	376.7	374.0	367.7	363.6	359.5
20°	410.5	406.9	400.6	391.6	378.5	364.9	357.7	353.2	349.6	343.3	341.5
22.5°	393.8	389.3	383.9	372.2	360.9	349.6	339.7	335.6	331.1	326.6	323.9
25°	380.7	374.0	368.1	353.7	342.4	332.9	326.6	319.8	313.5	310.8	309.9
27.5°	360.4	356.4	350.5	337.0	326.6	316.2	310.4	305.9	299.1	295.9	293.2
30°	347.4	339.2	332.5	321.6	311.3	300.0	294.6	289.2	285.1	281.0	277.9
32.5°	329.8	323.4	318.0	307.2	296.8	286.5	280.6	272.5	270.2	267.1	263.4
35°	312.6	308.6	302.7	291.0	279.7	272.5	266.2	258.5	255.8	253.5	250.4
37.5°	296.4	290.5	286.5	275.2	265.3	256.7	251.7	245.4	243.6	240.9	238.6
40°	282.4	276.5	272.5	261.2	250.8	241.8	238.6	232.3	229.6	226.5	225.1
42.5°	266.6	261.6	256.2	248.1	237.3	228.3	221.9	218.3	214.7	213.4	210.7
45°	249.9	245.4	241.3	232.3	221.0	214.7	209.3	204.4	201.6	199.4	197.6
47.5°	235.5	231.4	226.0	216.1	207.1	201.2	195.8	190.8	188.1	185.4	183.2
50°	218.8	216.5	210.7	201.2	192.6	185.9	180.9	176.4	174.6	171.4	167.8
52.5°	203.9	199.8	194.9	187.2	179.5	171.4	164.7	161.9	158.8	157.0	153.8
55°	186.3	183.6	178.2	171.4	163.3	156.5	151.6	148.0	143.9	142.1	138.0
57.5°	171.4	166.5	163.8	155.2	147.5	140.7	137.1	133.5	129.0	126.3	124.5
60°	155.2	150.7	146.6	139.4	134.0	126.8	121.3	118.2	115.0	111.4	109.6
62.5°	139.4	135.8	130.8	125.0	118.2	112.3	108.3	103.8	102.0	98.3	97.0
65°	122.3	119.5	115.5	108.7	103.3	98.3	94.3	90.7	88.9	87.5	86.6
67.5°	106.9	103.3	100.6	94.7	88.9	84.8	82.6	80.3	78.0	76.7	75.3
70°	91.1	88.4	85.7	80.3	76.2	72.6	70.8	69.0	67.7	66.3	65.0
72.5°	74.9	73.5	70.8	67.2	64.1	61.4	60.0	57.7	56.4	54.1	53.2
75°	61.8	59.5	58.2	55.0	52.3	50.1	48.3	45.6	43.8	42.9	42.4
77.5°	48.7	47.8	46.0	43.3	42.0	39.7	37.0	36.1	35.2	35.2	34.7
80°	36.5	35.2	33.8	31.6	30.2	28.4	28.4	28.4	28.0	28.4	28.0
82.5°	24.8	23.9	23.0	21.7	21.2	21.2	21.7	21.7	21.7	21.7	21.7
85°	14.4	14.4	14.4	14.9	14.4	14.4	14.9	15.3	14.9	14.9	14.4
87.5°	6.8	6.8	7.2	7.2	7.7	7.7	7.7	7.7	7.7	7.7	8.1
90°	8.4	9.2	9.9	12.1	14.4	16.7	19.0	18.2	19.0	19.7	20.5
92.5°	38.7	45.6	52.4	76.7	116.9	156.4	141.2	105.5	75.2	58.5	50.9
95°	69.1	83.9	98.7	163.2	276.3	400.8	450.2	365.1	273.3	185.2	145.0
97.5°	79.7	96.1	112.4	176.1	307.5	517.0	692.3	715.9	627.8	473.7	373.5
100°	91.1	105.9	120.7	173.8	286.2	485.9	718.9	868.5	895.0	833.5	744.7
102.5°	104.0	117.3	130.6	176.9	268.0	440.3	669.6	876.1	983.9	996.8	954.2
105°	118.4	130.2	142.0	183.0	261.1	404.6	610.4	828.2	986.9	1062.8	1077.2
107.5°	134.4	145.4	156.4	192.8	259.6	378.8	558.0	759.9	941.3	1060.5	1119.7
110°	150.3	161.0	171.6	205.7	263.4	365.1	514.7	696.1	870.0	1009.7	1105.3

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	167.0	177.2	187.5	218.6	271.0	357.6	485.9	640.7	799.4	942.9	1052.9
115°	183.7	194.0	204.2	233.1	279.4	356.8	466.9	598.2	738.6	870.7	982.3
117.5°	200.4	209.9	219.4	248.2	290.0	357.6	454.0	570.1	691.6	808.5	911.0
120°	216.4	225.8	235.3	262.7	302.1	360.6	445.6	548.9	655.9	758.4	849.5
122.5°	230.8	241.0	251.3	277.8	313.5	365.9	440.3	531.4	627.8	718.2	800.9
125°	245.2	255.4	265.7	292.3	325.7	371.2	435.7	517.0	603.5	686.3	759.1
127.5°	258.9	269.2	279.4	305.2	335.5	377.3	433.5	503.3	581.5	656.7	723.5
130°	271.0	281.2	291.5	316.6	345.4	383.4	431.2	492.7	561.0	629.3	690.8
132.5°	282.4	292.2	302.1	326.4	354.5	387.9	430.4	482.8	542.0	603.5	659.7
135°	292.3	302.6	312.8	336.3	362.1	392.5	429.7	474.5	525.3	579.2	628.6
137.5°	301.4	310.9	320.4	343.1	368.2	395.5	428.2	466.9	509.4	554.9	599.0
140°	309.0	318.5	328.0	350.0	372.7	398.6	427.4	460.0	495.7	534.4	570.9
142.5°	316.6	325.3	334.0	355.3	377.3	400.8	425.9	454.0	482.8	514.7	545.1
145°	322.6	331.4	340.1	359.8	380.3	401.6	424.4	448.7	472.9	498.0	522.3
147.5°	330.2	337.8	345.4	363.6	382.6	401.6	422.1	443.3	464.6	485.1	505.6
150°	336.3	343.2	350.0	367.4	383.4	401.6	419.0	438.0	455.5	472.9	488.9
152.5°	342.4	348.8	355.3	369.7	384.9	399.3	415.3	432.0	447.1	461.6	475.2
155°	349.2	354.5	359.8	372.7	384.9	397.8	410.7	425.9	438.8	450.9	462.3
157.5°	355.3	359.5	363.6	374.3	385.6	395.5	406.9	419.0	429.7	440.3	449.4
160°	359.8	363.6	367.4	376.5	385.6	394.0	402.3	412.2	422.1	430.4	438.0
162.5°	363.6	366.6	369.7	377.3	384.9	391.0	397.8	405.4	413.0	419.8	426.6
165°	366.7	369.4	372.0	378.1	383.4	387.9	393.2	399.3	405.4	409.9	415.3
167.5°	369.7	371.6	373.5	378.1	382.6	384.9	388.7	393.2	398.6	402.3	405.4
170°	372.0	372.8	373.5	377.3	380.3	381.9	384.1	387.9	391.7	394.0	397.0
172.5°	373.5	373.9	374.3	377.3	379.6	379.6	380.3	382.6	385.6	387.2	389.4
175°	374.3	374.6	375.0	376.5	378.1	377.3	377.3	378.8	380.3	381.1	382.6
177.5°	375.0	375.0	375.0	375.8	377.3	375.8	375.0	375.8	376.5	377.3	378.1
180°	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	498.0	498.5	497.1	494.4	494.0	494.9	497.6	496.7	494.4	498.5	494.9
5°	470.5	468.3	467.3	468.3	465.5	464.2	466.9	465.5	466.9	467.3	468.7
7.5°	443.9	444.3	441.6	442.1	438.5	439.4	439.4	439.4	440.7	441.6	443.4
10°	420.9	421.8	418.6	419.1	416.4	414.6	415.9	418.6	418.6	418.6	419.5
12.5°	402.4	398.3	396.1	395.6	392.5	391.6	394.3	395.2	397.4	397.4	398.8
15°	379.4	378.5	376.7	376.7	369.0	370.8	371.7	374.9	379.4	375.8	376.7
17.5°	358.6	356.4	354.1	353.2	352.3	349.6	353.2	352.8	355.5	355.9	357.3
20°	340.1	338.3	333.8	334.3	335.2	331.1	333.4	333.4	336.1	338.8	341.9
22.5°	322.1	320.3	318.0	318.9	316.2	315.3	315.3	317.6	320.7	323.0	322.5
25°	308.1	305.0	303.6	302.2	300.9	301.8	300.4	302.7	305.0	306.3	305.0
27.5°	292.3	291.0	288.3	286.9	284.7	285.6	286.5	288.3	289.6	289.6	291.0
30°	277.0	275.2	274.3	272.9	272.9	271.1	271.6	273.4	274.7	276.1	277.9
32.5°	262.1	260.7	259.4	259.4	258.5	258.0	257.6	260.3	260.3	263.0	263.0
35°	249.9	247.7	247.7	245.4	246.3	245.9	245.0	246.8	247.2	249.0	248.6
37.5°	236.4	236.4	235.5	233.2	231.4	231.9	234.1	234.1	235.5	235.0	236.4
40°	222.8	221.9	221.9	220.6	220.1	219.7	220.1	220.6	222.8	222.4	222.8
42.5°	209.3	209.8	207.5	207.5	207.5	206.2	206.6	207.1	208.0	208.9	210.2
45°	196.2	195.3	194.9	194.0	193.1	193.5	193.1	194.9	194.4	195.3	196.7
47.5°	182.2	180.9	180.4	178.6	178.6	179.5	179.1	180.4	180.9	182.2	181.3
50°	168.7	166.9	165.6	166.0	163.3	164.2	164.2	165.6	166.9	167.4	168.3
52.5°	152.9	152.5	152.0	149.8	149.3	148.9	149.3	149.8	151.6	152.9	153.4
55°	137.6	137.1	134.4	133.5	132.2	132.2	133.1	133.5	136.7	137.1	138.9
57.5°	123.6	122.3	119.1	118.6	118.6	118.6	117.3	119.1	120.0	122.3	122.3
60°	108.3	108.3	105.6	105.6	106.0	105.6	105.6	106.0	106.0	107.8	108.7
62.5°	96.1	95.6	95.6	94.7	94.3	94.7	94.3	94.3	94.7	96.1	97.4
65°	85.3	84.8	84.4	83.9	83.0	83.0	83.5	84.4	84.4	85.3	85.7
67.5°	74.9	74.9	74.0	74.0	73.5	73.1	73.5	73.1	74.9	74.9	75.3
70°	64.5	64.1	62.7	62.3	60.9	61.4	61.4	62.7	63.2	64.1	65.0
72.5°	51.9	51.9	51.0	50.1	50.5	49.6	49.6	50.1	50.1	51.4	51.9
75°	42.9	42.0	41.5	42.0	41.5	42.4	41.5	41.5	42.4	42.4	42.4
77.5°	35.2	35.2	34.7	34.7	35.2	34.7	35.2	35.2	35.2	34.7	35.2
80°	28.9	28.4	28.4	28.4	28.0	28.0	28.0	28.0	28.0	28.0	28.0
82.5°	21.7	21.7	21.2	21.7	21.7	21.2	21.7	21.2	21.2	21.7	21.7
85°	14.4	15.3	14.4	14.4	14.9	14.9	15.3	14.9	15.3	14.4	14.9
87.5°	7.7	8.1	8.1	7.7	7.7	8.1	8.1	8.1	8.6	7.7	8.1
90°	21.2	22.0	21.3	22.0	22.8	22.0	22.8	22.0	21.3	22.0	21.2
92.5°	48.2	45.5	44.0	41.0	41.8	40.2	41.8	41.0	44.0	45.5	48.2
95°	131.4	117.7	103.2	96.4	91.1	88.1	91.1	96.4	103.2	117.7	131.4
97.5°	330.2	287.0	236.1	207.2	189.0	180.7	189.0	207.2	236.1	287.0	330.2
100°	690.8	636.9	560.2	504.8	475.2	476.0	475.2	504.8	560.2	636.9	690.8
102.5°	925.0	895.8	840.4	799.4	775.8	753.8	775.8	799.4	840.4	895.8	925.0
105°	1067.4	1057.5	1022.6	993.7	969.4	965.6	969.4	993.7	1022.6	1057.5	1067.4
107.5°	1130.0	1140.2	1135.7	1122.0	1112.1	1103.8	1112.1	1122.0	1135.7	1140.2	1130.0
110°	1131.9	1158.5	1179.7	1185.8	1184.3	1182.7	1184.3	1185.8	1179.7	1158.5	1131.9

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1089.0	1125.1	1168.3	1190.3	1197.9	1198.7	1197.9	1190.3	1168.3	1125.1	1089.0
115°	1023.7	1065.1	1122.0	1155.4	1170.6	1174.4	1170.6	1155.4	1122.0	1065.1	1023.7
117.5°	953.9	996.8	1056.0	1093.2	1115.9	1121.3	1115.9	1093.2	1056.0	996.8	953.9
120°	887.8	926.2	986.1	1028.6	1046.9	1051.4	1046.9	1028.6	986.1	926.2	887.8
122.5°	835.8	870.7	922.4	959.6	980.1	986.1	980.1	959.6	922.4	870.7	835.8
125°	789.5	819.9	868.5	901.9	920.8	926.2	920.8	901.9	868.5	819.9	789.5
127.5°	751.6	779.6	823.7	852.5	870.0	874.5	870.0	852.5	823.7	779.6	751.6
130°	716.6	742.4	782.7	810.0	826.0	832.0	826.0	810.0	782.7	742.4	716.6
132.5°	684.0	708.3	745.5	772.8	786.5	790.3	786.5	772.8	745.5	708.3	684.0
135°	650.2	671.8	709.0	731.8	745.5	750.8	745.5	731.8	709.0	671.8	650.2
137.5°	618.4	637.7	669.6	693.1	704.5	709.0	704.5	693.1	669.6	637.7	618.4
140°	587.2	603.5	632.4	653.6	665.8	665.0	665.8	653.6	632.4	603.5	587.2
142.5°	558.8	572.4	595.9	614.1	624.8	624.0	624.8	614.1	595.9	572.4	558.8
145°	533.3	544.3	563.3	579.2	585.3	586.8	585.3	579.2	563.3	544.3	533.3
147.5°	513.6	521.5	536.7	548.1	554.2	554.9	554.2	548.1	536.7	521.5	513.6
150°	496.1	503.3	514.7	523.1	527.6	527.6	527.6	523.1	514.7	503.3	496.1
152.5°	480.9	486.6	495.0	502.6	504.8	504.8	504.8	502.6	495.0	486.6	480.9
155°	466.8	471.4	478.3	484.3	485.9	486.6	485.9	484.3	478.3	471.4	466.8
157.5°	453.2	457.0	463.1	467.6	469.2	469.2	469.2	467.6	463.1	457.0	453.2
160°	440.6	443.3	448.7	453.2	453.2	452.5	453.2	453.2	448.7	443.3	440.6
162.5°	428.9	431.2	434.2	438.0	438.0	437.3	438.0	438.0	434.2	431.2	428.9
165°	417.2	419.0	422.1	425.1	424.4	424.4	424.4	425.1	422.1	419.0	417.2
167.5°	406.9	408.4	409.9	412.2	411.5	411.5	411.5	412.2	409.9	408.4	406.9
170°	397.8	398.6	399.3	400.8	400.1	400.1	400.1	400.8	399.3	398.6	397.8
172.5°	389.8	390.2	390.2	391.7	390.2	389.4	390.2	391.7	390.2	390.2	389.8
175°	382.6	382.6	382.6	383.4	382.6	381.9	382.6	383.4	382.6	382.6	382.6
177.5°	378.1	378.1	377.3	378.1	376.5	376.5	376.5	378.1	377.3	378.1	378.1
180°	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	498.5	500.3	498.5	494.9	498.5	500.7	503.0	506.6	508.4	508.4	511.1
5°	470.1	473.7	472.3	471.4	475.0	477.3	480.9	485.4	490.4	493.5	497.1
7.5°	444.8	447.0	449.3	449.3	452.9	457.9	463.3	468.7	475.0	479.5	482.2
10°	422.7	424.5	425.8	427.7	433.1	438.5	445.7	452.5	457.9	462.8	467.3
12.5°	401.5	404.2	407.4	408.7	412.8	419.5	426.3	434.4	443.0	448.0	452.5
15°	381.2	382.5	386.1	390.2	393.8	401.0	409.6	418.2	425.4	433.1	437.1
17.5°	360.4	360.9	370.4	368.1	379.8	386.6	391.1	399.2	411.0	417.3	423.6
20°	340.1	344.6	348.7	351.0	357.3	364.9	378.0	384.3	393.8	399.7	405.1
22.5°	324.3	331.1	331.1	336.5	339.7	346.9	356.4	368.6	378.9	383.0	390.7
25°	310.4	313.5	318.9	320.7	326.6	332.9	339.2	352.3	363.6	369.0	374.4
27.5°	292.3	296.4	303.6	303.6	311.3	318.0	325.7	334.3	345.5	353.2	359.1
30°	278.3	282.4	285.6	290.5	293.7	300.0	313.5	319.8	329.8	336.5	343.7
32.5°	265.3	268.4	271.1	276.5	280.1	287.4	294.6	305.9	314.4	320.7	328.4
35°	250.8	254.0	257.6	261.6	267.1	273.8	280.6	290.1	298.6	304.5	310.8
37.5°	237.3	239.5	245.0	247.7	252.2	258.5	267.1	277.0	284.7	289.2	295.5
40°	224.2	226.0	230.1	235.0	238.2	243.1	252.2	260.7	270.2	275.6	280.6
42.5°	210.2	212.5	216.1	221.0	226.0	231.4	236.4	246.3	254.9	259.4	264.8
45°	198.0	199.4	202.1	207.1	212.0	216.1	223.8	232.8	240.9	244.5	250.4
47.5°	183.6	185.0	189.0	191.3	196.7	202.1	209.8	218.8	226.0	229.6	235.0
50°	168.7	170.1	172.8	177.7	181.3	187.2	194.0	201.6	210.7	215.6	218.8
52.5°	154.3	157.0	159.2	163.3	167.8	173.7	180.0	187.2	194.9	199.8	203.5
55°	139.8	142.1	144.8	147.1	152.5	157.9	165.1	171.9	178.6	183.2	187.2
57.5°	123.6	126.8	129.5	134.0	138.0	142.6	150.7	156.1	164.2	167.4	171.0
60°	109.6	112.8	115.0	118.6	122.3	128.1	133.5	140.3	147.1	151.1	155.6
62.5°	97.9	99.2	100.6	104.2	107.8	113.2	118.6	125.4	132.6	134.9	138.5
65°	86.2	87.5	89.8	92.9	95.6	98.8	104.7	110.1	116.8	120.4	121.8
67.5°	76.2	77.6	78.0	80.3	82.6	86.2	89.3	94.7	101.0	103.3	106.0
70°	65.0	67.2	67.7	69.5	70.4	72.6	76.2	80.3	85.3	89.3	91.6
72.5°	51.9	55.0	55.9	58.6	60.0	62.3	65.0	68.1	71.3	73.1	74.9
75°	42.4	43.3	43.8	46.0	48.3	51.4	52.8	54.6	57.3	59.5	61.4
77.5°	35.2	35.6	36.1	36.1	36.5	38.3	41.1	43.3	45.1	46.0	47.4
80°	28.4	28.0	28.0	28.4	28.4	28.4	29.3	32.5	33.4	35.6	35.2
82.5°	22.1	21.2	21.7	21.2	21.2	21.2	21.2	21.7	21.7	23.0	23.9
85°	14.4	14.9	14.4	14.4	14.0	14.4	14.0	14.0	13.5	13.5	13.1
87.5°	7.7	8.1	7.7	7.7	7.2	7.7	7.2	7.2	6.8	6.8	5.9
90°	20.5	19.7	19.0	18.2	19.0	16.7	14.4	12.1	9.9	9.2	8.4
92.5°	50.9	58.5	75.2	105.5	141.2	156.4	116.9	76.7	52.4	45.6	38.7
95°	145.0	185.2	273.3	365.1	450.2	400.8	276.3	163.2	98.7	83.9	69.1
97.5°	373.5	473.7	627.8	715.9	692.3	517.0	307.5	176.1	112.4	96.1	79.7
100°	744.7	833.5	895.0	868.5	718.9	485.9	286.2	173.8	120.7	105.9	91.1
102.5°	954.2	996.8	983.9	876.1	669.6	440.3	268.0	176.9	130.6	117.3	104.0
105°	1077.2	1062.8	986.9	828.2	610.4	404.6	261.1	183.0	142.0	130.2	118.4
107.5°	1119.7	1060.5	941.3	759.9	558.0	378.8	259.6	192.8	156.4	145.4	134.4
110°	1105.3	1009.7	870.0	696.1	514.7	365.1	263.4	205.7	171.6	161.0	150.3

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1052.9	942.9	799.4	640.7	485.9	357.6	271.0	218.6	187.5	177.2	167.0
115°	982.3	870.7	738.6	598.2	466.9	356.8	279.4	233.1	204.2	194.0	183.7
117.5°	911.0	808.5	691.6	570.1	454.0	357.6	290.0	248.2	219.4	209.9	200.4
120°	849.5	758.4	655.9	548.9	445.6	360.6	302.1	262.7	235.3	225.8	216.4
122.5°	800.9	718.2	627.8	531.4	440.3	365.9	313.5	277.8	251.3	241.0	230.8
125°	759.1	686.3	603.5	517.0	435.7	371.2	325.7	292.3	265.7	255.4	245.2
127.5°	723.5	656.7	581.5	503.3	433.5	377.3	335.5	305.2	279.4	269.2	258.9
130°	690.8	629.3	561.0	492.7	431.2	383.4	345.4	316.6	291.5	281.2	271.0
132.5°	659.7	603.5	542.0	482.8	430.4	387.9	354.5	326.4	302.1	292.2	282.4
135°	628.6	579.2	525.3	474.5	429.7	392.5	362.1	336.3	312.8	302.6	292.3
137.5°	599.0	554.9	509.4	466.9	428.2	395.5	368.2	343.1	320.4	310.9	301.4
140°	570.9	534.4	495.7	460.0	427.4	398.6	372.7	350.0	328.0	318.5	309.0
142.5°	545.1	514.7	482.8	454.0	425.9	400.8	377.3	355.3	334.0	325.3	316.6
145°	522.3	498.0	472.9	448.7	424.4	401.6	380.3	359.8	340.1	331.4	322.6
147.5°	505.6	485.1	464.6	443.3	422.1	401.6	382.6	363.6	345.4	337.8	330.2
150°	488.9	472.9	455.5	438.0	419.0	401.6	383.4	367.4	350.0	343.2	336.3
152.5°	475.2	461.6	447.1	432.0	415.3	399.3	384.9	369.7	355.3	348.8	342.4
155°	462.3	450.9	438.8	425.9	410.7	397.8	384.9	372.7	359.8	354.5	349.2
157.5°	449.4	440.3	429.7	419.0	406.9	395.5	385.6	374.3	363.6	359.5	355.3
160°	438.0	430.4	422.1	412.2	402.3	394.0	385.6	376.5	367.4	363.6	359.8
162.5°	426.6	419.8	413.0	405.4	397.8	391.0	384.9	377.3	369.7	366.6	363.6
165°	415.3	409.9	405.4	399.3	393.2	387.9	383.4	378.1	372.0	369.4	366.7
167.5°	405.4	402.3	398.6	393.2	388.7	384.9	382.6	378.1	373.5	371.6	369.7
170°	397.0	394.0	391.7	387.9	384.1	381.9	380.3	377.3	373.5	372.8	372.0
172.5°	389.4	387.2	385.6	382.6	380.3	379.6	379.6	377.3	374.3	373.9	373.5
175°	382.6	381.1	380.3	378.8	377.3	377.3	378.1	376.5	375.0	374.6	374.3
177.5°	378.1	377.3	376.5	375.8	375.0	375.8	377.3	375.8	375.0	375.0	375.0
180°	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0	375.0

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	526.9	526.9	526.9	526.9
2.5°	513.4	516.5	522.8	528.2
5°	502.5	507.5	517.0	526.4
7.5°	489.5	497.1	509.3	522.4
10°	476.8	486.7	501.6	517.0
12.5°	464.2	474.6	490.4	510.2
15°	449.3	460.1	479.1	503.0
17.5°	436.2	450.7	467.8	491.7
20°	422.2	433.1	455.2	480.4
22.5°	404.6	422.7	443.4	470.1
25°	390.7	406.4	427.2	457.4
27.5°	373.5	392.0	417.3	443.9
30°	359.5	374.9	398.3	430.4
32.5°	343.3	361.3	385.7	417.3
35°	328.9	344.2	367.2	399.2
37.5°	311.7	328.4	354.1	382.5
40°	296.8	313.1	337.4	364.0
42.5°	278.8	295.9	320.3	342.8
45°	264.4	280.1	299.5	320.3
47.5°	246.8	263.4	282.4	296.8
50°	231.0	246.3	261.2	273.4
52.5°	213.8	227.8	241.3	250.4
55°	198.0	208.9	219.7	226.0
57.5°	179.5	189.9	198.9	202.5
60°	163.3	171.9	177.7	181.8
62.5°	146.2	152.5	157.0	159.2
65°	129.5	134.0	136.2	138.5
67.5°	112.3	116.4	117.7	120.4
70°	94.3	98.8	99.7	101.0
72.5°	80.7	80.7	82.6	84.4
75°	64.5	65.4	66.3	66.3
77.5°	50.5	50.5	51.4	51.9
80°	37.0	37.4	37.4	37.0
82.5°	25.3	26.2	25.3	24.8
85°	14.0	15.8	14.9	14.9
87.5°	5.9	5.9	6.8	5.9
90°	6.8	4.6	3.0	1.5
92.5°	31.1	24.3	16.7	11.4
95°	49.3	36.4	28.1	25.8
97.5°	60.0	48.6	41.8	41.0
100°	72.9	62.2	56.9	56.2
102.5°	88.1	78.2	73.6	72.1
105°	104.0	94.9	90.3	88.1
107.5°	120.7	111.6	107.0	104.8
110°	137.4	129.1	125.3	123.0

TEST NUMBER: P1012542

CATALOG NUMBER: S123RDIP-B340D805UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	154.1	145.8	142.0	139.7
115°	170.8	163.2	158.7	155.6
117.5°	186.0	179.2	175.4	171.6
120°	201.9	194.3	190.5	188.3
122.5°	217.1	208.8	205.0	202.7
125°	230.8	222.4	217.9	216.4
127.5°	242.9	234.6	229.3	227.0
130°	255.1	246.0	239.1	236.9
132.5°	266.5	255.1	247.5	244.4
135°	276.3	264.9	256.6	253.6
137.5°	285.4	273.3	264.9	261.9
140°	293.8	281.6	274.1	270.3
142.5°	301.4	290.8	282.4	279.4
145°	309.7	298.3	291.5	289.2
147.5°	317.3	307.5	300.6	299.1
150°	325.7	315.8	309.7	309.0
152.5°	333.3	324.9	318.8	318.8
155°	340.9	333.3	328.7	328.7
157.5°	347.7	340.9	337.1	336.3
160°	354.5	348.4	345.4	345.4
162.5°	359.1	354.5	352.2	352.2
165°	363.6	359.8	358.3	359.1
167.5°	367.4	364.4	363.6	364.4
170°	370.5	368.2	367.4	368.9
172.5°	372.7	371.2	371.2	372.0
175°	374.3	372.7	373.5	374.3
177.5°	375.0	374.3	375.0	375.8
180°	375.0	375.0	375.0	375.0

(END OF REPORT)