

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012548

Luminaire Tested: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012548
REPORT IS A COMBINATION OF REPORTS P993315 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D805UB50-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3998.0 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32		
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34	27		
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29	24		
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	28	27	25	20		
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	25	24	22	18		
5	66	55	47	42	59	50	43	38	40	36	32	31	28	26	23	21	19	16		
6	61	49	42	36	55	45	38	33	36	32	28	28	25	22	21	19	17	14		
7	56	45	37	32	51	41	34	29	33	28	25	26	22	20	19	17	15	13		
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11		
9	49	37	30	25	44	34	27	23	28	23	20	22	18	16	16	14	12	10		
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11	9		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5481	5481	5481	5481
5°	5486	6313	5500	4683
10°	5437	7621	5461	4091
15°	5381	8649	5381	3607
20°	5270	9329	5300	3200
25°	5190	8864	5180	2920
30°	5096	6141	5086	2645
35°	4982	3943	4960	2439
40°	4842	2784	4818	2233
45°	4596	2228	4591	2033
50°	4296	1864	4282	1800
55°	3957	1536	3926	1525
60°	3625	1269	3590	1297
65°	3234	1016	3256	1100
70°	2877	706	2954	889
75°	2438	524	2537	684
80°	1944	347	2106	512
85°	1383	164	1508	319

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7318 cd/sqm

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.3
10°-20°	156.5	3.9
20°-30°	246.6	6.2
30°-40°	256.4	6.4
40°-50°	219.3	5.5
50°-60°	167.2	4.2
60°-70°	107.1	2.7
70°-80°	51.3	1.3
80°-90°	15.5	0.4
90°-100°	196.8	4.9
100°-110°	576.2	14.4
110°-120°	562.6	14.1
120°-130°	448.1	11.2
130°-140°	353.5	8.8
140°-150°	263.7	6.6
150°-160°	183.9	4.6
160°-170°	108.0	2.7
170°-180°	35.1	0.9
0°-30°	453.1	11.3
0°-40°	709.5	17.7
0°-60°	1096.0	27.4
0°-90°	1270.0	31.8
90°-120°	1335.6	33.4
90°-150°	2400.9	60.1
90°-180°	2728.0	68.2
0°-180°	3998.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	509	605	510	449	509	48
15°	486	859	486	358	486	137
25°	442	886	441	292	442	204
35°	386	384	384	238	386	241
45°	310	205	309	187	310	238
55°	218	129	217	128	218	196
65°	134	74	135	80	134	134
75°	64	31	67	41	64	69
85°	14	7	16	14	14	16
90°	2	21	2	21	2	3
95°	25	85	25	85	25	26
105°	85	934	85	934	85	90
115°	150	1136	150	1136	150	149
125°	209	896	209	896	209	186
135°	245	726	245	726	245	189
145°	280	568	280	568	280	175
155°	318	471	318	471	318	146
165°	347	410	347	410	347	98
175°	362	369	362	369	362	34
180°	363	363	363	363	363	

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	510.5	514.0	516.6	518.4	522.7	525.4	527.5	531.5	531.5	532.3	534.1
5°	508.8	516.2	521.4	528.4	537.6	541.9	548.0	553.3	560.7	564.6	568.5
7.5°	504.9	515.3	526.2	536.7	550.2	558.9	565.0	578.5	588.1	599.9	609.1
10°	499.6	514.0	528.0	544.1	562.4	575.5	584.7	602.5	620.8	637.4	651.4
12.5°	493.1	510.5	530.6	550.2	575.9	589.0	603.8	626.1	652.2	673.2	691.9
15°	486.1	506.2	528.8	552.8	585.1	603.4	624.8	651.8	681.0	711.1	736.8
17.5°	475.2	500.5	525.8	560.7	598.6	609.5	627.8	664.9	701.1	728.1	759.5
20°	464.3	492.7	524.5	555.9	596.9	622.1	639.1	678.4	717.2	749.9	780.0
22.5°	454.3	483.9	517.1	556.7	595.1	620.4	641.8	682.7	727.7	764.3	801.3
25°	442.1	474.3	511.0	548.5	595.1	614.3	637.8	685.4	732.9	775.2	821.0
27.5°	429.0	461.7	497.9	536.3	579.0	607.3	630.4	681.4	739.4	784.8	831.9
30°	415.9	449.5	484.4	518.8	566.8	593.8	620.4	676.6	742.9	794.8	831.0
32.5°	403.3	431.6	466.1	499.6	547.2	576.8	606.9	671.8	744.2	787.8	805.3
35°	385.8	415.5	443.4	479.1	527.1	556.3	591.6	671.4	738.6	765.6	756.9
37.5°	369.7	394.6	421.2	453.0	502.2	540.2	576.8	660.1	719.8	721.5	672.3
40°	351.8	372.3	394.6	428.1	481.3	518.8	558.5	642.6	685.8	660.1	573.3
42.5°	331.3	349.7	367.1	399.8	457.8	499.6	542.4	620.8	636.5	577.2	487.0
45°	309.5	324.4	340.5	374.9	432.9	474.3	517.1	587.3	571.1	487.4	401.5
47.5°	286.9	299.5	315.2	346.6	406.3	448.6	489.2	539.3	498.3	408.5	336.6
50°	264.2	274.2	289.5	321.8	379.3	417.7	455.2	487.9	430.3	350.5	278.2
52.5°	242.0	249.8	265.5	293.0	348.8	385.4	412.4	425.1	366.7	289.5	241.5
55°	218.4	227.1	237.6	265.5	320.9	347.9	365.8	365.4	305.2	245.5	199.7
57.5°	195.8	203.6	212.8	240.7	285.6	303.9	319.1	311.7	254.6	201.0	171.3
60°	175.7	180.1	190.1	213.6	247.6	263.3	272.1	259.4	208.0	169.6	141.7
62.5°	153.9	158.3	166.5	188.8	209.7	218.0	225.4	209.3	171.8	138.2	121.2
65°	133.8	139.5	144.7	162.6	174.0	184.0	183.1	169.6	134.3	112.5	98.5
67.5°	116.4	118.6	122.9	133.8	139.1	146.5	146.9	131.7	108.1	91.6	83.3
70°	97.7	99.8	102.9	108.1	111.6	113.4	112.5	99.0	81.5	71.5	64.1
72.5°	81.5	81.1	83.3	83.3	86.8	86.3	83.7	73.2	61.9	53.6	49.3
75°	64.1	64.5	65.0	64.1	62.8	61.0	58.9	51.0	43.6	39.7	35.8
77.5°	50.1	49.3	49.7	46.6	44.9	43.2	40.1	36.2	30.1	29.2	27.5
80°	35.8	35.3	34.9	33.6	29.6	27.9	25.7	23.5	22.2	21.4	20.9
82.5°	24.0	24.0	23.1	20.5	18.3	17.0	16.6	15.7	14.4	14.4	14.0
85°	14.4	14.0	13.1	10.5	9.2	9.2	9.2	9.2	8.3	8.3	7.8
87.5°	5.7	5.2	3.9	3.9	3.5	3.5	3.5	3.1	3.1	2.6	2.6
90°	1.5	2.9	4.4	6.6	8.1	8.8	9.5	11.7	13.9	16.2	18.4
92.5°	11.0	16.2	23.5	30.1	37.4	44.0	50.7	74.1	113.1	151.2	136.5
95°	25.0	27.2	35.2	47.7	66.8	81.1	95.4	157.8	267.2	387.6	435.3
97.5°	39.6	40.4	47.0	58.0	77.1	92.9	108.7	170.3	297.3	499.9	669.5
100°	54.3	55.1	60.2	70.5	88.1	102.4	116.7	168.1	276.8	469.8	695.2
102.5°	69.7	71.2	75.6	85.2	100.6	113.4	126.3	171.1	259.2	425.8	647.5
105°	85.2	87.4	91.8	100.6	114.5	125.9	137.3	176.9	252.5	391.3	590.2
107.5°	101.3	103.5	107.9	116.7	129.9	140.6	151.2	186.5	251.1	366.3	539.6
110°	118.9	121.1	124.8	132.9	145.4	155.6	165.9	199.0	254.7	353.1	497.7

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	135.1	137.3	141.0	149.0	161.5	171.4	181.3	211.4	262.1	345.8	469.8
115°	150.5	153.4	157.8	165.2	177.7	187.6	197.5	225.4	270.2	345.0	451.5
117.5°	165.9	169.6	173.3	179.9	193.8	203.0	212.2	240.1	280.4	345.8	439.0
120°	182.1	184.3	187.9	195.3	209.2	218.4	227.6	254.0	292.2	348.7	430.9
122.5°	196.0	198.2	201.9	210.0	223.2	233.1	243.0	268.7	303.2	353.9	425.8
125°	209.2	210.7	215.1	223.2	237.1	247.0	256.9	282.6	314.9	359.0	421.4
127.5°	219.5	221.7	226.8	234.9	250.3	260.2	270.2	295.1	324.5	364.9	419.2
130°	229.1	231.3	237.9	246.7	262.1	272.0	281.9	306.1	334.0	370.7	417.0
132.5°	236.4	239.3	246.7	257.7	273.1	282.6	292.2	315.7	342.8	375.1	416.3
135°	245.2	248.1	256.2	267.2	282.6	292.6	302.5	325.2	350.2	379.5	415.5
137.5°	253.3	256.2	264.3	276.0	291.5	300.6	309.8	331.8	356.1	382.5	414.1
140°	261.4	265.0	272.4	284.1	298.8	308.0	317.1	338.4	360.5	385.4	413.3
142.5°	270.2	273.1	281.2	291.5	306.1	314.6	323.0	343.6	364.9	387.6	411.9
145°	279.7	281.9	288.5	299.5	312.0	320.4	328.9	348.0	367.8	388.4	410.4
147.5°	289.2	290.7	297.3	306.9	319.3	326.6	334.0	351.7	370.0	388.4	408.2
150°	298.8	299.5	305.4	314.9	325.2	331.8	338.4	355.3	370.7	388.4	405.2
152.5°	308.3	308.3	314.2	322.3	331.1	337.4	343.6	357.5	372.2	386.2	401.6
155°	317.9	317.9	322.3	329.6	337.7	342.8	348.0	360.5	372.2	384.7	397.2
157.5°	325.2	326.0	329.6	336.2	343.6	347.6	351.7	361.9	372.9	382.5	393.5
160°	334.0	334.0	337.0	342.8	348.0	351.6	355.3	364.1	372.9	381.0	389.1
162.5°	340.6	340.6	342.8	347.2	351.7	354.6	357.5	364.9	372.2	378.1	384.7
165°	347.2	346.5	348.0	351.7	354.6	357.2	359.7	365.6	370.7	375.1	380.3
167.5°	352.4	351.7	352.4	355.3	357.5	359.4	361.2	365.6	370.0	372.2	375.9
170°	356.8	355.3	356.1	358.3	359.7	360.4	361.2	364.9	367.8	369.3	371.5
172.5°	359.7	359.0	359.0	360.5	361.2	361.5	361.9	364.9	367.1	367.1	367.8
175°	361.9	361.2	360.5	361.9	361.9	362.3	362.7	364.1	365.6	364.9	364.9
177.5°	363.4	362.7	361.9	362.7	362.7	362.7	362.7	363.4	364.9	363.4	362.7
180°	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	537.6	537.6	541.5	545.4	543.2	544.5	549.3	547.6	551.1	550.6	552.0
5°	578.1	582.9	586.8	595.1	596.4	595.1	603.4	605.6	609.5	604.7	606.9
7.5°	623.9	633.9	643.5	655.7	659.6	660.5	664.9	671.0	676.2	666.6	671.4
10°	668.4	683.6	703.2	714.1	723.7	727.2	730.7	734.6	740.7	746.4	742.0
12.5°	716.3	738.6	757.3	776.9	788.7	787.4	797.4	800.0	804.8	806.1	807.9
15°	755.6	786.9	798.7	827.9	830.5	839.3	850.6	860.6	861.9	859.3	859.3
17.5°	793.0	820.1	841.0	864.6	869.3	876.8	891.1	895.9	897.7	897.2	897.2
20°	823.6	841.4	876.8	896.4	904.2	913.8	923.8	929.9	931.3	933.0	930.4
22.5°	843.6	870.7	899.4	915.6	922.1	925.6	932.1	933.9	931.7	932.1	932.6
25°	859.3	885.9	903.4	907.7	907.3	902.9	898.1	889.8	889.0	885.5	878.5
27.5°	863.7	873.7	871.5	853.7	835.8	834.0	805.3	789.6	771.7	774.3	764.3
30°	840.1	827.1	796.1	750.8	732.0	701.5	669.2	635.7	622.6	608.2	634.8
32.5°	782.6	735.9	681.0	622.1	590.8	563.7	529.3	504.9	490.9	479.1	501.8
35°	695.8	623.0	550.2	494.4	468.7	444.3	412.0	399.8	382.4	384.1	386.3
37.5°	584.2	504.0	449.1	394.1	377.1	367.1	343.6	324.8	318.7	317.0	317.0
40°	479.6	413.7	364.9	321.8	308.7	300.4	281.6	272.9	266.4	264.6	266.8
42.5°	396.7	340.5	302.6	273.8	264.6	254.2	246.3	235.4	234.1	231.1	235.0
45°	333.1	284.3	255.9	235.0	227.1	223.2	214.5	208.0	205.3	204.9	208.0
47.5°	282.5	244.6	219.7	206.7	200.6	196.6	189.2	186.6	184.0	184.9	183.5
50°	237.2	208.8	192.7	180.9	177.0	173.1	168.3	165.7	164.4	164.4	163.9
52.5°	203.6	180.1	169.6	158.7	157.0	154.8	149.5	147.8	145.6	145.2	146.9
55°	174.4	158.3	147.8	141.3	139.5	135.2	133.0	130.8	129.5	128.6	129.1
57.5°	149.1	136.9	129.9	124.3	121.2	119.5	115.5	115.1	114.2	114.2	113.8
60°	128.2	119.5	111.2	107.7	105.5	103.3	102.9	100.3	99.0	99.8	99.4
62.5°	108.6	101.6	96.8	92.9	91.6	89.8	88.5	87.6	86.3	86.8	86.8
65°	90.7	85.0	81.5	78.0	77.6	75.9	75.4	74.6	74.6	74.1	75.0
67.5°	74.6	70.6	67.6	65.4	64.1	64.5	62.8	61.5	61.5	61.0	62.3
70°	59.3	57.1	54.1	51.4	49.7	49.7	47.5	47.1	47.1	47.1	46.6
72.5°	45.8	41.9	40.5	39.7	39.7	39.7	38.8	38.8	38.4	38.8	38.4
75°	34.0	33.6	32.7	32.3	32.3	31.8	31.4	31.4	31.4	31.4	31.4
77.5°	26.6	26.6	25.7	25.3	25.3	25.3	24.9	24.9	24.4	24.4	24.4
80°	19.6	19.6	18.7	18.7	18.7	18.3	18.3	18.3	18.7	18.3	18.3
82.5°	13.5	13.5	13.1	13.5	13.1	12.6	12.6	12.6	12.2	12.6	12.6
85°	7.8	7.8	7.4	7.0	7.4	7.4	7.0	7.4	7.0	7.4	7.0
87.5°	3.1	2.6	2.6	2.6	2.2	2.6	2.2	2.2	2.6	2.2	2.6
90°	17.6	18.4	19.1	19.8	20.6	21.3	20.6	21.3	22.0	21.3	22.0
92.5°	102.0	72.7	56.5	49.2	46.6	44.0	42.6	39.6	40.4	38.9	40.4
95°	353.1	264.3	179.1	140.2	127.0	113.8	99.8	93.2	88.1	85.2	88.1
97.5°	692.3	607.1	458.1	361.2	319.4	277.5	228.3	200.4	182.8	174.7	182.8
100°	839.9	865.5	806.1	720.2	668.0	615.9	541.8	488.2	459.6	460.3	459.6
102.5°	847.2	951.4	963.9	922.8	894.6	866.3	812.7	773.0	750.3	729.0	750.3
105°	800.9	954.4	1027.8	1041.7	1032.2	1022.7	988.9	961.0	937.5	933.8	937.5
107.5°	734.9	910.3	1025.6	1082.9	1092.8	1102.7	1098.3	1085.1	1075.5	1067.4	1075.5
110°	673.2	841.3	976.4	1068.9	1094.6	1120.3	1140.8	1146.7	1145.3	1143.8	1145.3

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	619.6	773.0	911.8	1018.2	1053.1	1088.0	1129.8	1151.1	1158.5	1159.2	1158.5
115°	578.5	714.3	842.1	950.0	990.0	1030.0	1085.1	1117.4	1132.0	1135.7	1132.0
117.5°	551.3	668.8	781.9	881.0	922.4	963.9	1021.2	1057.2	1079.2	1084.3	1079.2
120°	530.8	634.3	733.4	821.5	858.6	895.6	953.6	994.8	1012.4	1016.8	1012.4
122.5°	513.9	607.1	694.5	774.5	808.3	842.1	892.0	927.9	947.8	953.6	947.8
125°	499.9	583.6	663.7	734.1	763.5	792.9	839.9	872.2	890.5	895.6	890.5
127.5°	486.7	562.3	635.0	699.6	726.8	754.0	796.5	824.4	841.3	845.7	841.3
130°	476.5	542.5	608.6	668.1	693.0	718.0	756.9	783.3	798.7	804.6	798.7
132.5°	466.9	524.2	583.6	638.0	661.4	684.9	720.9	747.4	760.6	764.2	760.6
135°	458.8	508.0	560.1	607.9	628.8	649.7	685.7	707.7	720.9	726.1	720.9
137.5°	451.5	492.6	536.7	579.2	598.0	616.7	647.5	670.3	681.3	685.7	681.3
140°	444.9	479.4	516.8	552.1	567.8	583.6	611.5	632.1	643.8	643.1	643.8
142.5°	439.0	466.9	497.7	527.1	540.3	553.5	576.3	593.9	604.2	603.5	604.2
145°	433.9	457.4	481.6	505.1	515.8	526.4	544.7	560.1	566.0	567.5	566.0
147.5°	428.7	449.3	469.1	488.9	496.6	504.4	519.0	530.0	535.9	536.7	535.9
150°	423.6	440.5	457.4	472.8	479.8	486.7	497.7	505.8	510.2	510.2	510.2
152.5°	417.7	432.4	446.4	459.6	465.1	470.6	478.7	486.0	488.2	488.2	488.2
155°	411.9	424.3	436.1	447.1	451.5	455.9	462.5	468.4	469.8	470.6	469.8
157.5°	405.2	415.5	425.8	434.6	438.3	442.0	447.8	452.2	453.7	453.7	453.7
160°	398.6	408.2	416.3	423.6	426.2	428.7	433.9	438.3	438.3	437.5	438.3
162.5°	392.0	399.4	406.0	412.6	414.8	417.0	419.9	423.6	423.6	422.9	423.6
165°	386.2	392.0	396.4	401.6	403.4	405.2	408.2	411.1	410.4	410.4	410.4
167.5°	380.3	385.4	389.1	392.0	393.5	395.0	396.4	398.6	397.9	397.9	397.9
170°	375.1	378.8	381.0	384.0	384.7	385.4	386.2	387.6	386.9	386.9	386.9
172.5°	370.0	372.9	374.4	376.6	377.0	377.3	377.3	378.8	377.3	376.6	377.3
175°	366.3	367.8	368.5	370.0	370.0	370.0	370.0	370.7	370.0	369.3	370.0
177.5°	363.4	364.1	364.9	365.6	365.6	365.6	364.9	365.6	364.1	364.1	364.1
180°	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	549.8	547.2	545.4	544.1	542.8	546.7	541.5	535.8	531.9	529.3	528.4
5°	607.3	601.7	596.9	592.9	593.8	593.8	584.7	574.6	565.9	561.1	555.9
7.5°	674.0	667.9	658.3	656.2	654.4	643.5	634.4	616.0	605.1	594.2	584.7
10°	740.3	732.4	723.3	720.2	715.9	702.4	688.4	664.9	651.4	631.3	618.7
12.5°	802.2	792.6	783.5	781.3	774.7	763.0	739.0	714.6	691.5	670.1	647.9
15°	854.1	851.5	837.5	828.8	814.4	798.3	793.0	759.9	730.7	708.5	668.4
17.5°	897.7	885.5	872.4	866.7	861.1	842.3	823.6	789.6	758.2	725.5	699.7
20°	932.6	919.0	909.9	901.6	899.0	877.6	848.0	817.9	783.5	746.8	713.3
22.5°	934.3	932.6	926.5	921.7	916.4	902.5	878.9	841.4	804.8	764.7	720.7
25°	898.1	895.5	912.9	908.6	912.1	906.8	894.2	862.8	820.1	773.0	728.5
27.5°	789.1	815.7	843.2	852.8	859.3	878.1	884.2	866.7	832.3	782.1	732.4
30°	640.9	676.2	720.7	744.7	763.0	797.8	843.2	848.9	832.7	792.6	731.6
32.5°	503.1	535.4	571.1	599.5	623.9	695.4	756.4	800.5	808.3	787.4	733.8
35°	405.5	419.4	453.4	480.5	513.6	574.6	646.6	717.6	765.6	768.2	727.2
37.5°	334.4	341.8	371.5	386.7	406.3	460.0	527.1	620.0	694.5	729.8	708.9
40°	276.8	293.9	310.9	319.6	333.5	370.6	435.1	507.9	600.3	665.7	680.6
42.5°	240.2	247.6	258.5	270.7	279.5	311.7	354.9	421.6	504.9	596.0	637.0
45°	211.9	214.5	225.8	233.7	242.8	265.5	296.0	351.8	425.1	514.9	584.7
47.5°	188.3	193.6	199.7	204.5	210.6	228.0	254.2	294.7	359.2	439.5	514.5
50°	167.4	170.5	178.3	180.5	184.9	197.1	217.1	248.1	301.3	365.4	443.0
52.5°	147.8	153.5	156.5	159.6	163.5	173.5	186.6	211.9	252.0	312.2	378.0
55°	132.5	134.3	138.6	141.3	144.3	151.3	162.6	181.4	212.8	260.7	323.1
57.5°	117.7	117.7	122.1	124.3	127.3	132.5	142.6	157.0	179.6	215.4	272.5
60°	102.0	102.5	105.9	108.6	109.4	114.7	122.9	134.3	151.7	177.9	224.5
62.5°	88.1	90.2	92.0	92.9	95.9	99.0	105.9	113.8	126.0	149.1	182.2
65°	76.3	76.7	78.0	78.9	80.2	83.7	88.9	94.2	104.6	121.6	148.7
67.5°	62.8	64.5	66.3	66.3	67.6	69.3	74.6	78.9	86.8	96.8	115.1
70°	47.1	48.0	50.6	51.9	53.6	56.7	59.3	61.9	68.0	75.4	89.4
72.5°	39.2	39.2	40.1	40.5	40.5	42.7	46.6	49.3	52.3	57.5	67.1
75°	31.4	31.4	32.7	32.3	33.1	34.0	34.4	36.2	37.9	41.9	47.5
77.5°	24.9	25.3	25.3	25.7	25.7	26.2	26.6	27.5	28.3	30.5	33.1
80°	18.3	18.7	18.7	19.2	19.2	19.6	20.1	20.5	21.4	22.2	23.5
82.5°	12.6	13.1	13.1	13.5	13.1	13.5	14.0	14.0	14.4	15.3	15.7
85°	7.4	7.4	7.8	7.4	7.4	7.4	7.8	7.8	8.3	9.6	9.6
87.5°	2.2	2.6	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.5	3.9
90°	21.3	20.6	21.3	20.6	19.8	19.1	18.4	17.6	18.4	16.2	13.9
92.5°	39.6	42.6	44.0	46.6	49.2	56.5	72.7	102.0	136.5	151.2	113.1
95°	93.2	99.8	113.8	127.0	140.2	179.1	264.3	353.1	435.3	387.6	267.2
97.5°	200.4	228.3	277.5	319.4	361.2	458.1	607.1	692.3	669.5	499.9	297.3
100°	488.2	541.8	615.9	668.0	720.2	806.1	865.5	839.9	695.2	469.8	276.8
102.5°	773.0	812.7	866.3	894.6	922.8	963.9	951.4	847.2	647.5	425.8	259.2
105°	961.0	988.9	1022.7	1032.2	1041.7	1027.8	954.4	800.9	590.2	391.3	252.5
107.5°	1085.1	1098.3	1102.7	1092.8	1082.9	1025.6	910.3	734.9	539.6	366.3	251.1
110°	1146.7	1140.8	1120.3	1094.6	1068.9	976.4	841.3	673.2	497.7	353.1	254.7

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1151.1	1129.8	1088.0	1053.1	1018.2	911.8	773.0	619.6	469.8	345.8	262.1
115°	1117.4	1085.1	1030.0	990.0	950.0	842.1	714.3	578.5	451.5	345.0	270.2
117.5°	1057.2	1021.2	963.9	922.4	881.0	781.9	668.8	551.3	439.0	345.8	280.4
120°	994.8	953.6	895.6	858.6	821.5	733.4	634.3	530.8	430.9	348.7	292.2
122.5°	927.9	892.0	842.1	808.3	774.5	694.5	607.1	513.9	425.8	353.9	303.2
125°	872.2	839.9	792.9	763.5	734.1	663.7	583.6	499.9	421.4	359.0	314.9
127.5°	824.4	796.5	754.0	726.8	699.6	635.0	562.3	486.7	419.2	364.9	324.5
130°	783.3	756.9	718.0	693.0	668.1	608.6	542.5	476.5	417.0	370.7	334.0
132.5°	747.4	720.9	684.9	661.4	638.0	583.6	524.2	466.9	416.3	375.1	342.8
135°	707.7	685.7	649.7	628.8	607.9	560.1	508.0	458.8	415.5	379.5	350.2
137.5°	670.3	647.5	616.7	598.0	579.2	536.7	492.6	451.5	414.1	382.5	356.1
140°	632.1	611.5	583.6	567.8	552.1	516.8	479.4	444.9	413.3	385.4	360.5
142.5°	593.9	576.3	553.5	540.3	527.1	497.7	466.9	439.0	411.9	387.6	364.9
145°	560.1	544.7	526.4	515.8	505.1	481.6	457.4	433.9	410.4	388.4	367.8
147.5°	530.0	519.0	504.4	496.6	488.9	469.1	449.3	428.7	408.2	388.4	370.0
150°	505.8	497.7	486.7	479.8	472.8	457.4	440.5	423.6	405.2	388.4	370.7
152.5°	486.0	478.7	470.6	465.1	459.6	446.4	432.4	417.7	401.6	386.2	372.2
155°	468.4	462.5	455.9	451.5	447.1	436.1	424.3	411.9	397.2	384.7	372.2
157.5°	452.2	447.8	442.0	438.3	434.6	425.8	415.5	405.2	393.5	382.5	372.9
160°	438.3	433.9	428.7	426.2	423.6	416.3	408.2	398.6	389.1	381.0	372.9
162.5°	423.6	419.9	417.0	414.8	412.6	406.0	399.4	392.0	384.7	378.1	372.2
165°	411.1	408.2	405.2	403.4	401.6	396.4	392.0	386.2	380.3	375.1	370.7
167.5°	398.6	396.4	395.0	393.5	392.0	389.1	385.4	380.3	375.9	372.2	370.0
170°	387.6	386.2	385.4	384.7	384.0	381.0	378.8	375.1	371.5	369.3	367.8
172.5°	378.8	377.3	377.3	377.0	376.6	374.4	372.9	370.0	367.8	367.1	367.1
175°	370.7	370.0	370.0	370.0	370.0	368.5	367.8	366.3	364.9	364.9	365.6
177.5°	365.6	364.9	365.6	365.6	365.6	364.9	364.1	363.4	362.7	363.4	364.9
180°	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	527.1	524.9	522.7	522.7	517.9	513.6	511.4	512.3	509.7	506.2	502.7
5°	550.2	541.5	539.7	534.9	528.4	519.3	514.5	510.1	504.9	497.9	491.4
7.5°	571.6	560.2	554.1	549.3	536.7	524.0	513.6	506.6	497.5	487.0	479.1
10°	599.5	578.5	572.0	561.1	543.2	525.4	513.1	501.8	489.2	477.0	466.5
12.5°	621.7	597.7	585.5	574.6	551.5	528.8	508.4	494.4	479.1	465.6	452.1
15°	647.0	620.0	598.6	585.5	556.3	528.8	505.7	486.1	469.1	452.5	440.8
17.5°	659.2	625.2	615.6	596.9	554.6	527.1	498.8	477.8	457.3	438.2	424.2
20°	678.4	638.7	614.7	602.1	564.6	524.0	490.9	466.9	445.6	425.1	410.3
22.5°	679.7	636.5	620.8	596.9	550.6	514.9	483.9	454.7	429.9	410.7	395.4
25°	676.6	632.6	610.8	591.6	553.3	509.7	470.0	441.2	416.8	394.6	376.7
27.5°	675.3	621.3	600.8	581.6	538.4	494.4	461.7	429.0	401.1	381.5	363.2
30°	673.6	609.1	584.2	562.0	522.3	482.6	443.4	415.1	388.5	363.6	345.3
32.5°	662.3	592.5	567.2	543.7	500.9	461.3	430.3	400.2	371.5	348.3	331.8
35°	658.8	577.2	544.1	518.8	477.0	441.6	409.0	384.1	357.1	334.0	314.3
37.5°	648.7	561.5	525.8	493.5	449.9	416.4	392.4	367.5	341.4	316.5	300.8
40°	631.3	543.2	502.7	469.6	424.6	390.6	368.4	350.1	324.4	302.1	283.0
42.5°	605.6	524.5	480.9	446.0	396.3	364.5	346.2	328.7	306.9	283.8	268.1
45°	575.9	499.6	459.1	420.3	369.7	338.8	319.6	309.1	289.1	269.4	251.1
47.5°	535.4	473.9	433.8	393.7	342.2	312.2	296.9	286.4	272.5	251.1	236.3
50°	484.4	440.8	402.8	367.1	315.2	286.4	271.2	263.3	251.6	236.3	221.9
52.5°	427.7	402.4	371.0	337.9	287.7	260.7	246.8	240.7	231.9	217.6	205.3
55°	370.6	359.7	338.3	305.6	259.0	236.7	224.5	216.7	210.1	199.7	189.2
57.5°	319.6	314.3	299.5	274.2	235.0	211.9	201.4	196.2	191.0	183.1	172.6
60°	266.8	272.5	257.2	244.6	208.8	188.8	179.6	174.0	171.3	164.4	157.8
62.5°	221.0	226.3	217.6	208.0	182.7	164.8	159.1	153.9	152.2	146.1	139.5
65°	179.6	186.2	179.6	174.4	159.1	144.3	137.3	134.7	133.0	129.1	123.8
67.5°	143.0	149.5	146.5	139.9	135.2	122.9	119.0	116.4	115.5	112.5	108.1
70°	107.7	116.8	117.7	113.8	109.4	103.8	101.1	100.3	98.1	95.5	92.9
72.5°	77.6	88.1	88.5	88.5	85.9	85.9	83.3	82.0	82.0	79.3	76.3
75°	57.1	64.1	65.0	65.8	67.1	68.4	66.7	66.7	66.3	63.7	62.3
77.5°	37.9	44.0	46.2	49.3	51.0	51.0	51.9	52.8	51.9	50.6	49.7
80°	24.4	28.8	31.4	33.1	35.8	37.1	38.4	38.8	37.9	37.5	36.2
82.5°	16.1	17.4	18.7	20.9	24.0	26.2	26.2	25.7	26.6	26.2	25.7
85°	9.2	10.0	10.5	10.9	12.6	14.8	15.3	15.7	16.6	15.7	14.8
87.5°	3.5	3.9	3.9	3.9	4.8	5.2	6.5	8.3	7.8	7.0	7.0
90°	11.7	9.5	8.8	8.1	6.6	4.4	2.9	1.5	2.9	4.4	6.6
92.5°	74.1	50.7	44.0	37.4	30.1	23.5	16.2	11.0	16.2	23.5	30.1
95°	157.8	95.4	81.1	66.8	47.7	35.2	27.2	25.0	27.2	35.2	47.7
97.5°	170.3	108.7	92.9	77.1	58.0	47.0	40.4	39.6	40.4	47.0	58.0
100°	168.1	116.7	102.4	88.1	70.5	60.2	55.1	54.3	55.1	60.2	70.5
102.5°	171.1	126.3	113.4	100.6	85.2	75.6	71.2	69.7	71.2	75.6	85.2
105°	176.9	137.3	125.9	114.5	100.6	91.8	87.4	85.2	87.4	91.8	100.6
107.5°	186.5	151.2	140.6	129.9	116.7	107.9	103.5	101.3	103.5	107.9	116.7
110°	199.0	165.9	155.6	145.4	132.9	124.8	121.1	118.9	121.1	124.8	132.9

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	211.4	181.3	171.4	161.5	149.0	141.0	137.3	135.1	137.3	141.0	149.0
115°	225.4	197.5	187.6	177.7	165.2	157.8	153.4	150.5	153.4	157.8	165.2
117.5°	240.1	212.2	203.0	193.8	179.9	173.3	169.6	165.9	169.6	173.3	179.9
120°	254.0	227.6	218.4	209.2	195.3	187.9	184.3	182.1	184.3	187.9	195.3
122.5°	268.7	243.0	233.1	223.2	210.0	201.9	198.2	196.0	198.2	201.9	210.0
125°	282.6	256.9	247.0	237.1	223.2	215.1	210.7	209.2	210.7	215.1	223.2
127.5°	295.1	270.2	260.2	250.3	234.9	226.8	221.7	219.5	221.7	226.8	234.9
130°	306.1	281.9	272.0	262.1	246.7	237.9	231.3	229.1	231.3	237.9	246.7
132.5°	315.7	292.2	282.6	273.1	257.7	246.7	239.3	236.4	239.3	246.7	257.7
135°	325.2	302.5	292.6	282.6	267.2	256.2	248.1	245.2	248.1	256.2	267.2
137.5°	331.8	309.8	300.6	291.5	276.0	264.3	256.2	253.3	256.2	264.3	276.0
140°	338.4	317.1	308.0	298.8	284.1	272.4	265.0	261.4	265.0	272.4	284.1
142.5°	343.6	323.0	314.6	306.1	291.5	281.2	273.1	270.2	273.1	281.2	291.5
145°	348.0	328.9	320.4	312.0	299.5	288.5	281.9	279.7	281.9	288.5	299.5
147.5°	351.7	334.0	326.6	319.3	306.9	297.3	290.7	289.2	290.7	297.3	306.9
150°	355.3	338.4	331.8	325.2	314.9	305.4	299.5	298.8	299.5	305.4	314.9
152.5°	357.5	343.6	337.4	331.1	322.3	314.2	308.3	308.3	308.3	314.2	322.3
155°	360.5	348.0	342.8	337.7	329.6	322.3	317.9	317.9	317.9	322.3	329.6
157.5°	361.9	351.7	347.6	343.6	336.2	329.6	326.0	325.2	326.0	329.6	336.2
160°	364.1	355.3	351.6	348.0	342.8	337.0	334.0	334.0	334.0	337.0	342.8
162.5°	364.9	357.5	354.6	351.7	347.2	342.8	340.6	340.6	340.6	342.8	347.2
165°	365.6	359.7	357.2	354.6	351.7	348.0	346.5	347.2	346.5	348.0	351.7
167.5°	365.6	361.2	359.4	357.5	355.3	352.4	351.7	352.4	351.7	352.4	355.3
170°	364.9	361.2	360.4	359.7	358.3	356.1	355.3	356.8	355.3	356.1	358.3
172.5°	364.9	361.9	361.5	361.2	360.5	359.0	359.0	359.7	359.0	359.0	360.5
175°	364.1	362.7	362.3	361.9	361.9	360.5	361.2	361.9	361.2	360.5	361.9
177.5°	363.4	362.7	362.7	362.7	362.7	361.9	362.7	363.4	362.7	361.9	362.7
180°	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	502.7	500.5	499.6	497.5	492.2	488.7	484.8	482.2	482.6	480.5	481.8
5°	487.0	486.6	483.5	479.1	471.7	467.8	460.8	457.3	455.6	456.0	453.4
7.5°	473.9	470.0	467.8	460.8	453.9	445.6	439.9	436.9	434.2	431.6	429.9
10°	459.1	455.6	452.1	444.7	435.1	427.3	419.4	416.4	412.4	410.7	409.4
12.5°	443.4	441.2	436.9	428.1	417.2	409.8	400.7	398.9	393.7	390.2	389.3
15°	429.0	427.7	419.8	409.8	398.9	391.5	383.7	378.4	369.7	371.5	368.4
17.5°	413.7	408.1	403.3	389.8	384.5	373.2	364.0	361.4	355.3	351.4	347.5
20°	396.7	393.3	387.2	378.4	365.8	352.7	345.7	341.4	337.9	331.8	330.0
22.5°	380.6	376.3	371.0	359.7	348.8	337.9	328.3	324.4	320.0	315.7	313.0
25°	368.0	361.4	355.8	341.8	330.9	321.8	315.7	309.1	303.0	300.4	299.5
27.5°	348.3	344.4	338.8	325.7	315.7	305.6	300.0	295.6	289.1	286.0	283.4
30°	335.7	327.9	321.3	310.9	300.8	289.9	284.7	279.5	275.5	271.6	268.6
32.5°	318.7	312.6	307.4	296.9	286.9	276.8	271.2	263.3	261.2	258.1	254.6
35°	302.1	298.2	292.5	281.2	270.3	263.3	257.2	249.8	247.2	245.0	242.0
37.5°	286.4	280.8	276.8	265.9	256.4	248.1	243.3	237.2	235.4	232.8	230.6
40°	272.9	267.3	263.3	252.4	242.4	233.7	230.6	224.5	221.9	218.9	217.6
42.5°	257.7	252.9	247.6	239.8	229.3	220.6	214.5	211.0	207.5	206.2	203.6
45°	241.5	237.2	233.2	224.5	213.6	207.5	202.3	197.5	194.9	192.7	191.0
47.5°	227.6	223.7	218.4	208.8	200.1	194.4	189.2	184.4	181.8	179.2	177.0
50°	211.5	209.3	203.6	194.4	186.2	179.6	174.8	170.5	168.7	165.7	162.2
52.5°	197.1	193.1	188.3	180.9	173.5	165.7	159.1	156.5	153.5	151.7	148.7
55°	180.1	177.4	172.2	165.7	157.8	151.3	146.5	143.0	139.1	137.3	133.4
57.5°	165.7	160.9	158.3	150.0	142.6	136.0	132.5	129.1	124.7	122.1	120.3
60°	150.0	145.6	141.7	134.7	129.5	122.5	117.3	114.2	111.2	107.7	105.9
62.5°	134.7	131.2	126.4	120.8	114.2	108.6	104.6	100.3	98.5	95.0	93.7
65°	118.2	115.5	111.6	105.1	99.8	95.0	91.1	87.6	85.9	84.6	83.7
67.5°	103.3	99.8	97.2	91.6	85.9	82.0	79.8	77.6	75.4	74.1	72.8
70°	88.1	85.5	82.8	77.6	73.7	70.2	68.4	66.7	65.4	64.1	62.8
72.5°	72.4	71.1	68.4	65.0	61.9	59.3	58.0	55.8	54.5	52.3	51.4
75°	59.7	57.5	56.2	53.2	50.6	48.4	46.6	44.0	42.3	41.4	41.0
77.5°	47.1	46.2	44.5	41.9	40.5	38.4	35.8	34.9	34.0	34.0	33.6
80°	35.3	34.0	32.7	30.5	29.2	27.5	27.5	27.5	27.0	27.5	27.0
82.5°	24.0	23.1	22.2	20.9	20.5	20.5	20.9	20.9	20.9	20.9	20.9
85°	14.0	14.0	14.0	14.4	14.0	14.0	14.4	14.8	14.4	14.4	14.0
87.5°	6.5	6.5	7.0	7.0	7.4	7.4	7.4	7.4	7.4	7.4	7.8
90°	8.1	8.8	9.5	11.7	13.9	16.2	18.4	17.6	18.4	19.1	19.8
92.5°	37.4	44.0	50.7	74.1	113.1	151.2	136.5	102.0	72.7	56.5	49.2
95°	66.8	81.1	95.4	157.8	267.2	387.6	435.3	353.1	264.3	179.1	140.2
97.5°	77.1	92.9	108.7	170.3	297.3	499.9	669.5	692.3	607.1	458.1	361.2
100°	88.1	102.4	116.7	168.1	276.8	469.8	695.2	839.9	865.5	806.1	720.2
102.5°	100.6	113.4	126.3	171.1	259.2	425.8	647.5	847.2	951.4	963.9	922.8
105°	114.5	125.9	137.3	176.9	252.5	391.3	590.2	800.9	954.4	1027.8	1041.7
107.5°	129.9	140.6	151.2	186.5	251.1	366.3	539.6	734.9	910.3	1025.6	1082.9
110°	145.4	155.6	165.9	199.0	254.7	353.1	497.7	673.2	841.3	976.4	1068.9

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	161.5	171.4	181.3	211.4	262.1	345.8	469.8	619.6	773.0	911.8	1018.2
115°	177.7	187.6	197.5	225.4	270.2	345.0	451.5	578.5	714.3	842.1	950.0
117.5°	193.8	203.0	212.2	240.1	280.4	345.8	439.0	551.3	668.8	781.9	881.0
120°	209.2	218.4	227.6	254.0	292.2	348.7	430.9	530.8	634.3	733.4	821.5
122.5°	223.2	233.1	243.0	268.7	303.2	353.9	425.8	513.9	607.1	694.5	774.5
125°	237.1	247.0	256.9	282.6	314.9	359.0	421.4	499.9	583.6	663.7	734.1
127.5°	250.3	260.2	270.2	295.1	324.5	364.9	419.2	486.7	562.3	635.0	699.6
130°	262.1	272.0	281.9	306.1	334.0	370.7	417.0	476.5	542.5	608.6	668.1
132.5°	273.1	282.6	292.2	315.7	342.8	375.1	416.3	466.9	524.2	583.6	638.0
135°	282.6	292.6	302.5	325.2	350.2	379.5	415.5	458.8	508.0	560.1	607.9
137.5°	291.5	300.6	309.8	331.8	356.1	382.5	414.1	451.5	492.6	536.7	579.2
140°	298.8	308.0	317.1	338.4	360.5	385.4	413.3	444.9	479.4	516.8	552.1
142.5°	306.1	314.6	323.0	343.6	364.9	387.6	411.9	439.0	466.9	497.7	527.1
145°	312.0	320.4	328.9	348.0	367.8	388.4	410.4	433.9	457.4	481.6	505.1
147.5°	319.3	326.6	334.0	351.7	370.0	388.4	408.2	428.7	449.3	469.1	488.9
150°	325.2	331.8	338.4	355.3	370.7	388.4	405.2	423.6	440.5	457.4	472.8
152.5°	331.1	337.4	343.6	357.5	372.2	386.2	401.6	417.7	432.4	446.4	459.6
155°	337.7	342.8	348.0	360.5	372.2	384.7	397.2	411.9	424.3	436.1	447.1
157.5°	343.6	347.6	351.7	361.9	372.9	382.5	393.5	405.2	415.5	425.8	434.6
160°	348.0	351.6	355.3	364.1	372.9	381.0	389.1	398.6	408.2	416.3	423.6
162.5°	351.7	354.6	357.5	364.9	372.2	378.1	384.7	392.0	399.4	406.0	412.6
165°	354.6	357.2	359.7	365.6	370.7	375.1	380.3	386.2	392.0	396.4	401.6
167.5°	357.5	359.4	361.2	365.6	370.0	372.2	375.9	380.3	385.4	389.1	392.0
170°	359.7	360.4	361.2	364.9	367.8	369.3	371.5	375.1	378.8	381.0	384.0
172.5°	361.2	361.5	361.9	364.9	367.1	367.1	367.8	370.0	372.9	374.4	376.6
175°	361.9	362.3	362.7	364.1	365.6	364.9	364.9	366.3	367.8	368.5	370.0
177.5°	362.7	362.7	362.7	363.4	364.9	363.4	362.7	363.4	364.1	364.9	365.6
180°	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	481.3	481.8	480.5	477.8	477.4	478.3	480.9	480.0	477.8	481.8	478.3
5°	454.7	452.5	451.7	452.5	449.9	448.6	451.2	449.9	451.2	451.7	453.0
7.5°	429.0	429.4	426.8	427.3	423.8	424.6	424.6	424.6	426.0	426.8	428.6
10°	406.8	407.6	404.6	405.0	402.4	400.7	402.0	404.6	404.6	404.6	405.5
12.5°	388.9	385.0	382.8	382.4	379.3	378.4	381.0	381.9	384.1	384.1	385.4
15°	366.7	365.8	364.0	364.0	356.6	358.4	359.2	362.3	366.7	363.2	364.0
17.5°	346.6	344.4	342.2	341.4	340.5	337.9	341.4	340.9	343.6	344.0	345.3
20°	328.7	327.0	322.6	323.1	323.9	320.0	322.2	322.2	324.8	327.4	330.5
22.5°	311.3	309.5	307.4	308.2	305.6	304.8	304.8	306.9	310.0	312.2	311.7
25°	297.8	294.7	293.4	292.1	290.8	291.7	290.4	292.5	294.7	296.0	294.7
27.5°	282.5	281.2	278.6	277.3	275.1	276.0	276.8	278.6	279.9	279.9	281.2
30°	267.7	265.9	265.1	263.8	263.8	262.0	262.5	264.2	265.5	266.8	268.6
32.5°	253.3	252.0	250.7	250.7	249.8	249.4	248.9	251.6	251.6	254.2	254.2
35°	241.5	239.4	239.4	237.2	238.0	237.6	236.7	238.5	238.9	240.7	240.2
37.5°	228.5	228.5	227.6	225.4	223.7	224.1	226.3	226.3	227.6	227.1	228.5
40°	215.4	214.5	214.5	213.2	212.8	212.3	212.8	213.2	215.4	214.9	215.4
42.5°	202.3	202.7	200.6	200.6	200.6	199.2	199.7	200.1	201.0	201.9	203.2
45°	189.7	188.8	188.3	187.5	186.6	187.0	186.6	188.3	187.9	188.8	190.1
47.5°	176.1	174.8	174.4	172.6	172.6	173.5	173.1	174.4	174.8	176.1	175.3
50°	163.1	161.3	160.0	160.4	157.8	158.7	158.7	160.0	161.3	161.7	162.6
52.5°	147.8	147.4	146.9	144.7	144.3	143.9	144.3	144.7	146.5	147.8	148.2
55°	133.0	132.5	129.9	129.1	127.7	127.7	128.6	129.1	132.1	132.5	134.3
57.5°	119.5	118.2	115.1	114.7	114.7	114.7	113.4	115.1	116.0	118.2	118.2
60°	104.6	104.6	102.0	102.0	102.5	102.0	102.0	102.5	102.5	104.2	105.1
62.5°	92.9	92.4	92.4	91.6	91.1	91.6	91.1	91.1	91.6	92.9	94.2
65°	82.4	82.0	81.5	81.1	80.2	80.2	80.7	81.5	81.5	82.4	82.8
67.5°	72.4	72.4	71.5	71.5	71.1	70.6	71.1	70.6	72.4	72.4	72.8
70°	62.3	61.9	60.6	60.2	58.9	59.3	59.3	60.6	61.0	61.9	62.8
72.5°	50.1	50.1	49.3	48.4	48.8	48.0	48.0	48.4	48.4	49.7	50.1
75°	41.4	40.5	40.1	40.5	40.1	41.0	40.1	40.1	41.0	41.0	41.0
77.5°	34.0	34.0	33.6	33.6	34.0	33.6	34.0	34.0	34.0	33.6	34.0
80°	27.9	27.5	27.5	27.5	27.0	27.0	27.0	27.0	27.0	27.0	27.0
82.5°	20.9	20.9	20.5	20.9	20.9	20.5	20.9	20.5	20.5	20.9	20.9
85°	14.0	14.8	14.0	14.0	14.4	14.4	14.8	14.4	14.8	14.0	14.4
87.5°	7.4	7.8	7.8	7.4	7.4	7.8	7.8	7.8	8.3	7.4	7.8
90°	20.6	21.3	20.6	21.3	22.0	21.3	22.0	21.3	20.6	21.3	20.6
92.5°	46.6	44.0	42.6	39.6	40.4	38.9	40.4	39.6	42.6	44.0	46.6
95°	127.0	113.8	99.8	93.2	88.1	85.2	88.1	93.2	99.8	113.8	127.0
97.5°	319.4	277.5	228.3	200.4	182.8	174.7	182.8	200.4	228.3	277.5	319.4
100°	668.0	615.9	541.8	488.2	459.6	460.3	459.6	488.2	541.8	615.9	668.0
102.5°	894.6	866.3	812.7	773.0	750.3	729.0	750.3	773.0	812.7	866.3	894.6
105°	1032.2	1022.7	988.9	961.0	937.5	933.8	937.5	961.0	988.9	1022.7	1032.2
107.5°	1092.8	1102.7	1098.3	1085.1	1075.5	1067.4	1075.5	1085.1	1098.3	1102.7	1092.8
110°	1094.6	1120.3	1140.8	1146.7	1145.3	1143.8	1145.3	1146.7	1140.8	1120.3	1094.6

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1053.1	1088.0	1129.8	1151.1	1158.5	1159.2	1158.5	1151.1	1129.8	1088.0	1053.1
115°	990.0	1030.0	1085.1	1117.4	1132.0	1135.7	1132.0	1117.4	1085.1	1030.0	990.0
117.5°	922.4	963.9	1021.2	1057.2	1079.2	1084.3	1079.2	1057.2	1021.2	963.9	922.4
120°	858.6	895.6	953.6	994.8	1012.4	1016.8	1012.4	994.8	953.6	895.6	858.6
122.5°	808.3	842.1	892.0	927.9	947.8	953.6	947.8	927.9	892.0	842.1	808.3
125°	763.5	792.9	839.9	872.2	890.5	895.6	890.5	872.2	839.9	792.9	763.5
127.5°	726.8	754.0	796.5	824.4	841.3	845.7	841.3	824.4	796.5	754.0	726.8
130°	693.0	718.0	756.9	783.3	798.7	804.6	798.7	783.3	756.9	718.0	693.0
132.5°	661.4	684.9	720.9	747.4	760.6	764.2	760.6	747.4	720.9	684.9	661.4
135°	628.8	649.7	685.7	707.7	720.9	726.1	720.9	707.7	685.7	649.7	628.8
137.5°	598.0	616.7	647.5	670.3	681.3	685.7	681.3	670.3	647.5	616.7	598.0
140°	567.8	583.6	611.5	632.1	643.8	643.1	643.8	632.1	611.5	583.6	567.8
142.5°	540.3	553.5	576.3	593.9	604.2	603.5	604.2	593.9	576.3	553.5	540.3
145°	515.8	526.4	544.7	560.1	566.0	567.5	566.0	560.1	544.7	526.4	515.8
147.5°	496.6	504.4	519.0	530.0	535.9	536.7	535.9	530.0	519.0	504.4	496.6
150°	479.8	486.7	497.7	505.8	510.2	510.2	510.2	505.8	497.7	486.7	479.8
152.5°	465.1	470.6	478.7	486.0	488.2	488.2	488.2	486.0	478.7	470.6	465.1
155°	451.5	455.9	462.5	468.4	469.8	470.6	469.8	468.4	462.5	455.9	451.5
157.5°	438.3	442.0	447.8	452.2	453.7	453.7	453.7	452.2	447.8	442.0	438.3
160°	426.2	428.7	433.9	438.3	438.3	437.5	438.3	438.3	433.9	428.7	426.2
162.5°	414.8	417.0	419.9	423.6	423.6	422.9	423.6	423.6	419.9	417.0	414.8
165°	403.4	405.2	408.2	411.1	410.4	410.4	410.4	411.1	408.2	405.2	403.4
167.5°	393.5	395.0	396.4	398.6	397.9	397.9	397.9	398.6	396.4	395.0	393.5
170°	384.7	385.4	386.2	387.6	386.9	386.9	386.9	387.6	386.2	385.4	384.7
172.5°	377.0	377.3	377.3	378.8	377.3	376.6	377.3	378.8	377.3	377.3	377.0
175°	370.0	370.0	370.0	370.7	370.0	369.3	370.0	370.7	370.0	370.0	370.0
177.5°	365.6	365.6	364.9	365.6	364.1	364.1	364.1	365.6	364.9	365.6	365.6
180°	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	481.8	483.5	481.8	478.3	481.8	483.9	486.1	489.6	491.4	491.4	494.0
5°	454.3	457.8	456.5	455.6	459.1	461.3	464.8	469.1	473.9	477.0	480.5
7.5°	429.9	432.1	434.2	434.2	437.7	442.5	447.8	453.0	459.1	463.4	466.1
10°	408.5	410.3	411.6	413.3	418.5	423.8	430.7	437.3	442.5	447.3	451.7
12.5°	388.0	390.6	393.7	395.0	398.9	405.5	412.0	419.8	428.1	432.9	437.3
15°	368.4	369.7	373.2	377.1	380.6	387.6	395.9	404.2	411.1	418.5	422.5
17.5°	348.3	348.8	357.9	355.8	367.1	373.6	378.0	385.8	397.2	403.3	409.4
20°	328.7	333.1	337.0	339.2	345.3	352.7	365.4	371.5	380.6	386.3	391.5
22.5°	313.5	320.0	320.0	325.2	328.3	335.3	344.4	356.2	366.2	370.1	377.6
25°	300.0	303.0	308.2	310.0	315.7	321.8	327.9	340.5	351.4	356.6	361.9
27.5°	282.5	286.4	293.4	293.4	300.8	307.4	314.8	323.1	334.0	341.4	347.0
30°	269.0	272.9	276.0	280.8	283.8	289.9	303.0	309.1	318.7	325.2	332.2
32.5°	256.4	259.4	262.0	267.3	270.7	277.7	284.7	295.6	303.9	310.0	317.4
35°	242.4	245.5	248.9	252.9	258.1	264.6	271.2	280.3	288.6	294.3	300.4
37.5°	229.3	231.5	236.7	239.4	243.7	249.8	258.1	267.7	275.1	279.5	285.6
40°	216.7	218.4	222.4	227.1	230.2	235.0	243.7	252.0	261.2	266.4	271.2
42.5°	203.2	205.3	208.8	213.6	218.4	223.7	228.5	238.0	246.3	250.7	255.9
45°	191.4	192.7	195.3	200.1	204.9	208.8	216.2	225.0	232.8	236.3	242.0
47.5°	177.4	178.8	182.7	184.9	190.1	195.3	202.7	211.5	218.4	221.9	227.1
50°	163.1	164.4	167.0	171.8	175.3	180.9	187.5	194.9	203.6	208.4	211.5
52.5°	149.1	151.7	153.9	157.8	162.2	167.9	174.0	180.9	188.3	193.1	196.6
55°	135.2	137.3	139.9	142.1	147.4	152.6	159.6	166.1	172.6	177.0	180.9
57.5°	119.5	122.5	125.1	129.5	133.4	137.8	145.6	150.8	158.7	161.7	165.2
60°	105.9	109.0	111.2	114.7	118.2	123.8	129.1	135.6	142.1	146.1	150.4
62.5°	94.6	95.9	97.2	100.7	104.2	109.4	114.7	121.2	128.2	130.4	133.8
65°	83.3	84.6	86.8	89.8	92.4	95.5	101.1	106.4	112.9	116.4	117.7
67.5°	73.7	75.0	75.4	77.6	79.8	83.3	86.3	91.6	97.7	99.8	102.5
70°	62.8	65.0	65.4	67.1	68.0	70.2	73.7	77.6	82.4	86.3	88.5
72.5°	50.1	53.2	54.1	56.7	58.0	60.2	62.8	65.8	68.9	70.6	72.4
75°	41.0	41.9	42.3	44.5	46.6	49.7	51.0	52.8	55.4	57.5	59.3
77.5°	34.0	34.4	34.9	34.9	35.3	37.1	39.7	41.9	43.6	44.5	45.8
80°	27.5	27.0	27.0	27.5	27.5	27.5	28.3	31.4	32.3	34.4	34.0
82.5°	21.4	20.5	20.9	20.5	20.5	20.5	20.5	20.9	20.9	22.2	23.1
85°	14.0	14.4	14.0	14.0	13.5	14.0	13.5	13.5	13.1	13.1	12.6
87.5°	7.4	7.8	7.4	7.4	7.0	7.4	7.0	7.0	6.5	6.5	5.7
90°	19.8	19.1	18.4	17.6	18.4	16.2	13.9	11.7	9.5	8.8	8.1
92.5°	49.2	56.5	72.7	102.0	136.5	151.2	113.1	74.1	50.7	44.0	37.4
95°	140.2	179.1	264.3	353.1	435.3	387.6	267.2	157.8	95.4	81.1	66.8
97.5°	361.2	458.1	607.1	692.3	669.5	499.9	297.3	170.3	108.7	92.9	77.1
100°	720.2	806.1	865.5	839.9	695.2	469.8	276.8	168.1	116.7	102.4	88.1
102.5°	922.8	963.9	951.4	847.2	647.5	425.8	259.2	171.1	126.3	113.4	100.6
105°	1041.7	1027.8	954.4	800.9	590.2	391.3	252.5	176.9	137.3	125.9	114.5
107.5°	1082.9	1025.6	910.3	734.9	539.6	366.3	251.1	186.5	151.2	140.6	129.9
110°	1068.9	976.4	841.3	673.2	497.7	353.1	254.7	199.0	165.9	155.6	145.4

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1018.2	911.8	773.0	619.6	469.8	345.8	262.1	211.4	181.3	171.4	161.5
115°	950.0	842.1	714.3	578.5	451.5	345.0	270.2	225.4	197.5	187.6	177.7
117.5°	881.0	781.9	668.8	551.3	439.0	345.8	280.4	240.1	212.2	203.0	193.8
120°	821.5	733.4	634.3	530.8	430.9	348.7	292.2	254.0	227.6	218.4	209.2
122.5°	774.5	694.5	607.1	513.9	425.8	353.9	303.2	268.7	243.0	233.1	223.2
125°	734.1	663.7	583.6	499.9	421.4	359.0	314.9	282.6	256.9	247.0	237.1
127.5°	699.6	635.0	562.3	486.7	419.2	364.9	324.5	295.1	270.2	260.2	250.3
130°	668.1	608.6	542.5	476.5	417.0	370.7	334.0	306.1	281.9	272.0	262.1
132.5°	638.0	583.6	524.2	466.9	416.3	375.1	342.8	315.7	292.2	282.6	273.1
135°	607.9	560.1	508.0	458.8	415.5	379.5	350.2	325.2	302.5	292.6	282.6
137.5°	579.2	536.7	492.6	451.5	414.1	382.5	356.1	331.8	309.8	300.6	291.5
140°	552.1	516.8	479.4	444.9	413.3	385.4	360.5	338.4	317.1	308.0	298.8
142.5°	527.1	497.7	466.9	439.0	411.9	387.6	364.9	343.6	323.0	314.6	306.1
145°	505.1	481.6	457.4	433.9	410.4	388.4	367.8	348.0	328.9	320.4	312.0
147.5°	488.9	469.1	449.3	428.7	408.2	388.4	370.0	351.7	334.0	326.6	319.3
150°	472.8	457.4	440.5	423.6	405.2	388.4	370.7	355.3	338.4	331.8	325.2
152.5°	459.6	446.4	432.4	417.7	401.6	386.2	372.2	357.5	343.6	337.4	331.1
155°	447.1	436.1	424.3	411.9	397.2	384.7	372.2	360.5	348.0	342.8	337.7
157.5°	434.6	425.8	415.5	405.2	393.5	382.5	372.9	361.9	351.7	347.6	343.6
160°	423.6	416.3	408.2	398.6	389.1	381.0	372.9	364.1	355.3	351.6	348.0
162.5°	412.6	406.0	399.4	392.0	384.7	378.1	372.2	364.9	357.5	354.6	351.7
165°	401.6	396.4	392.0	386.2	380.3	375.1	370.7	365.6	359.7	357.2	354.6
167.5°	392.0	389.1	385.4	380.3	375.9	372.2	370.0	365.6	361.2	359.4	357.5
170°	384.0	381.0	378.8	375.1	371.5	369.3	367.8	364.9	361.2	360.4	359.7
172.5°	376.6	374.4	372.9	370.0	367.8	367.1	367.1	364.9	361.9	361.5	361.2
175°	370.0	368.5	367.8	366.3	364.9	364.9	365.6	364.1	362.7	362.3	361.9
177.5°	365.6	364.9	364.1	363.4	362.7	363.4	364.9	363.4	362.7	362.7	362.7
180°	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7	362.7

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	509.2	509.2	509.2	509.2
2.5°	496.1	499.2	505.3	510.5
5°	485.7	490.5	499.6	508.8
7.5°	473.0	480.5	492.2	504.9
10°	460.8	470.4	484.8	499.6
12.5°	448.6	458.7	473.9	493.1
15°	434.2	444.7	463.0	486.1
17.5°	421.6	435.5	452.1	475.2
20°	408.1	418.5	439.9	464.3
22.5°	391.1	408.5	428.6	454.3
25°	377.6	392.8	412.9	442.1
27.5°	361.0	378.9	403.3	429.0
30°	347.5	362.3	385.0	415.9
32.5°	331.8	349.2	372.8	403.3
35°	317.8	332.7	354.9	385.8
37.5°	301.3	317.4	342.2	369.7
40°	286.9	302.6	326.1	351.8
42.5°	269.4	286.0	309.5	331.3
45°	255.5	270.7	289.5	309.5
47.5°	238.5	254.6	272.9	286.9
50°	223.2	238.0	252.4	264.2
52.5°	206.7	220.2	233.2	242.0
55°	191.4	201.9	212.3	218.4
57.5°	173.5	183.5	192.3	195.8
60°	157.8	166.1	171.8	175.7
62.5°	141.3	147.4	151.7	153.9
65°	125.1	129.5	131.7	133.8
67.5°	108.6	112.5	113.8	116.4
70°	91.1	95.5	96.4	97.7
72.5°	78.0	78.0	79.8	81.5
75°	62.3	63.2	64.1	64.1
77.5°	48.8	48.8	49.7	50.1
80°	35.8	36.2	36.2	35.8
82.5°	24.4	25.3	24.4	24.0
85°	13.5	15.3	14.4	14.4
87.5°	5.7	5.7	6.5	5.7
90°	6.6	4.4	2.9	1.5
92.5°	30.1	23.5	16.2	11.0
95°	47.7	35.2	27.2	25.0
97.5°	58.0	47.0	40.4	39.6
100°	70.5	60.2	55.1	54.3
102.5°	85.2	75.6	71.2	69.7
105°	100.6	91.8	87.4	85.2
107.5°	116.7	107.9	103.5	101.3
110°	132.9	124.8	121.1	118.9

TEST NUMBER: P1012548

CATALOG NUMBER: S123RDIP-B340D805UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	149.0	141.0	137.3	135.1
115°	165.2	157.8	153.4	150.5
117.5°	179.9	173.3	169.6	165.9
120°	195.3	187.9	184.3	182.1
122.5°	210.0	201.9	198.2	196.0
125°	223.2	215.1	210.7	209.2
127.5°	234.9	226.8	221.7	219.5
130°	246.7	237.9	231.3	229.1
132.5°	257.7	246.7	239.3	236.4
135°	267.2	256.2	248.1	245.2
137.5°	276.0	264.3	256.2	253.3
140°	284.1	272.4	265.0	261.4
142.5°	291.5	281.2	273.1	270.2
145°	299.5	288.5	281.9	279.7
147.5°	306.9	297.3	290.7	289.2
150°	314.9	305.4	299.5	298.8
152.5°	322.3	314.2	308.3	308.3
155°	329.6	322.3	317.9	317.9
157.5°	336.2	329.6	326.0	325.2
160°	342.8	337.0	334.0	334.0
162.5°	347.2	342.8	340.6	340.6
165°	351.7	348.0	346.5	347.2
167.5°	355.3	352.4	351.7	352.4
170°	358.3	356.1	355.3	356.8
172.5°	360.5	359.0	359.0	359.7
175°	361.9	360.5	361.2	361.9
177.5°	362.7	361.9	362.7	363.4
180°	362.7	362.7	362.7	362.7

(END OF REPORT)