

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012554

Luminaire Tested: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012554
REPORT IS A COMBINATION OF REPORTS P993321 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5843.0 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45
1	95	91	88	84	87	83	80	77	68	66	64	53	52	51	40	39	39
2	87	80	75	70	79	73	68	64	60	56	53	47	45	43	36	35	33
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29
4	73	63	55	50	66	58	51	46	47	43	39	38	35	32	29	27	25
5	67	56	49	43	61	51	45	40	43	38	34	34	31	28	26	24	22
6	62	51	43	37	56	46	40	35	38	33	30	31	27	25	24	22	20
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18
8	53	41	34	29	48	38	32	27	32	27	23	26	22	20	20	18	16
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9510	9510	9510	9510
5°	9518	10953	9542	8126
10°	9434	13222	9475	7098
15°	9336	15006	9336	6258
20°	9145	16186	9196	5551
25°	9004	15378	8987	5066
30°	8841	10655	8823	4590
35°	8645	6841	8606	4232
40°	8401	4831	8359	3876
45°	7977	3865	7965	3528
50°	7454	3234	7430	3122
55°	6867	2665	6811	2647
60°	6289	2203	6227	2251
65°	5613	1763	5649	1908
70°	4989	1225	5124	1543
75°	4230	909	4401	1186
80°	3366	603	3654	889
85°	2401	286	2613	554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 12696 cd/sqm

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	1.5
10°-20°	271.6	4.6
20°-30°	427.8	7.3
30°-40°	444.8	7.6
40°-50°	380.6	6.5
50°-60°	290.1	5.0
60°-70°	185.9	3.2
70°-80°	89.1	1.5
80°-90°	26.1	0.4
90°-100°	262.6	4.5
100°-110°	768.8	13.2
110°-120°	750.8	12.8
120°-130°	597.9	10.2
130°-140°	471.8	8.1
140°-150°	351.9	6.0
150°-160°	245.4	4.2
160°-170°	144.1	2.5
170°-180°	46.9	0.8
0°-30°	786.1	13.5
0°-40°	1231.0	21.1
0°-60°	1901.6	32.5
0°-90°	2202.7	37.7
90°-120°	1782.3	30.5
90°-150°	3203.9	54.8
90°-180°	3640.0	62.3
0°-180°	5843.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	884	884	884	884	884	
5°	883	1049	885	778	883	84
15°	843	1491	843	622	843	237
25°	767	1536	766	506	767	353
35°	669	666	666	412	669	419
45°	537	356	536	324	537	414
55°	379	223	376	222	379	340
65°	232	129	234	139	232	232
75°	111	54	116	71	111	120
85°	25	13	27	25	25	28
90°	2	28	2	28	2	4
95°	33	114	33	114	33	35
105°	114	1246	114	1246	114	121
115°	201	1516	201	1516	201	199
125°	279	1195	279	1195	279	248
135°	327	969	327	969	327	253
145°	373	757	373	757	373	234
155°	424	628	424	628	424	195
165°	463	548	463	548	463	131
175°	483	493	483	493	483	46
180°	484	484	484	484	484	

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	885.8	891.8	896.4	899.4	907.0	911.5	915.3	922.1	922.1	923.6	926.6
5°	882.8	895.6	904.7	916.8	932.7	940.2	950.8	959.9	972.8	979.6	986.4
7.5°	876.0	894.1	913.0	931.2	954.6	969.7	980.3	1003.8	1020.4	1040.9	1056.7
10°	866.9	891.8	916.0	944.0	975.8	998.5	1014.4	1045.4	1077.2	1105.9	1130.1
12.5°	855.5	885.8	920.6	954.6	999.2	1021.9	1047.7	1086.2	1131.6	1167.9	1200.5
15°	843.4	878.2	917.6	959.2	1015.1	1046.9	1084.0	1130.9	1181.5	1233.7	1278.4
17.5°	824.5	868.4	912.3	972.8	1038.6	1057.5	1089.3	1153.6	1216.3	1263.2	1317.7
20°	805.6	854.8	910.0	964.5	1035.6	1079.4	1108.9	1177.0	1244.3	1301.1	1353.3
22.5°	788.2	839.6	897.1	966.0	1032.5	1076.4	1113.5	1184.6	1262.5	1326.0	1390.3
25°	767.0	823.0	886.5	951.6	1032.5	1065.8	1106.7	1189.1	1271.6	1344.9	1424.4
27.5°	744.3	801.1	863.8	930.4	1004.5	1053.7	1093.8	1182.3	1282.9	1361.6	1443.3
30°	721.6	779.9	840.4	900.2	983.4	1030.3	1076.4	1174.0	1289.0	1379.0	1441.8
32.5°	699.7	748.9	808.6	866.9	949.3	1000.8	1053.0	1165.7	1291.2	1366.9	1397.1
35°	669.4	720.9	769.3	831.3	914.5	965.2	1026.5	1164.9	1281.4	1328.3	1313.2
37.5°	641.5	684.6	730.7	785.9	871.4	937.2	1000.8	1145.2	1248.9	1251.9	1166.4
40°	610.4	646.0	684.6	742.8	835.1	900.2	969.0	1115.0	1189.9	1145.2	994.7
42.5°	574.9	606.7	636.9	693.6	794.3	866.9	941.0	1077.2	1104.4	1001.5	844.9
45°	537.1	562.8	590.8	650.5	751.1	823.0	897.1	1018.9	990.9	845.7	696.7
47.5°	497.7	519.7	546.9	601.4	705.0	778.4	848.7	935.7	864.6	708.8	584.0
50°	458.4	475.8	502.3	558.2	658.1	724.7	789.7	846.4	746.6	608.2	482.6
52.5°	419.8	433.4	460.7	508.3	605.1	668.7	715.6	737.5	636.2	502.3	419.1
55°	379.0	394.1	412.3	460.7	556.7	603.6	634.6	633.9	529.5	425.9	346.4
57.5°	339.6	353.3	369.1	417.6	495.5	527.2	553.7	540.9	441.8	348.7	297.3
60°	304.8	312.4	329.8	370.7	429.7	456.9	472.0	450.1	360.8	294.3	245.8
62.5°	267.0	274.6	289.0	327.5	363.8	378.2	391.1	363.1	298.0	239.8	210.3
65°	232.2	242.1	251.1	282.1	301.8	319.2	317.7	294.3	233.0	195.2	171.0
67.5°	202.0	205.7	213.3	232.2	241.3	254.2	254.9	228.4	187.6	158.9	144.5
70°	169.4	173.2	178.5	187.6	193.6	196.7	195.2	171.7	141.5	124.1	111.2
72.5°	141.5	140.7	144.5	144.5	150.5	149.8	145.2	127.1	107.4	93.0	85.5
75°	111.2	112.0	112.7	111.2	108.9	105.9	102.1	88.5	75.6	68.8	62.0
77.5°	87.0	85.5	86.2	80.9	77.9	74.9	69.6	62.8	52.2	50.7	47.7
80°	62.0	61.3	60.5	58.2	51.4	48.4	44.6	40.8	38.6	37.1	36.3
82.5°	41.6	41.6	40.1	35.6	31.8	29.5	28.7	27.2	25.0	25.0	24.2
85°	25.0	24.2	22.7	18.2	15.9	15.9	15.9	15.9	14.4	14.4	13.6
87.5°	9.8	9.1	6.8	6.8	6.1	6.1	6.1	5.3	5.3	4.5	4.5
90°	2.0	3.9	5.9	8.8	10.8	11.8	12.7	15.7	18.6	21.6	24.5
92.5°	14.7	21.6	31.3	40.2	50.0	58.8	67.6	98.9	150.9	201.8	182.2
95°	33.3	36.2	47.0	63.7	89.1	108.2	127.4	210.6	356.6	517.3	580.9
97.5°	52.9	53.9	62.7	77.4	102.9	124.0	145.0	227.3	396.8	667.1	893.4
100°	72.5	73.5	80.3	94.0	117.6	136.7	155.8	224.3	369.3	627.0	927.7
102.5°	93.1	95.0	100.9	113.6	134.2	151.4	168.5	228.3	345.8	568.2	864.1
105°	113.6	116.6	122.5	134.2	152.8	168.0	183.2	236.1	337.0	522.2	787.6
107.5°	135.2	138.1	144.0	155.8	173.4	187.6	201.8	248.8	335.0	488.8	720.0
110°	158.7	161.6	166.5	177.3	194.0	207.7	221.4	265.5	339.9	471.2	664.2

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	180.3	183.2	188.1	198.9	215.5	228.8	242.0	282.1	349.7	461.4	627.0
115°	200.8	204.7	210.6	220.4	237.1	250.3	263.5	300.8	360.5	460.4	602.5
117.5°	221.4	226.3	231.2	240.0	258.6	270.8	283.1	320.3	374.2	461.4	585.8
120°	243.0	245.9	250.8	260.6	279.2	291.4	303.7	339.0	389.9	465.3	575.1
122.5°	261.6	264.5	269.4	280.2	297.8	311.0	324.3	358.6	404.6	472.2	568.2
125°	279.2	281.2	287.0	297.8	316.4	329.6	342.9	377.2	420.3	479.1	562.3
127.5°	292.9	295.9	302.7	313.5	334.1	347.3	360.5	393.8	433.0	486.9	559.4
130°	305.7	308.6	317.4	329.2	349.7	363.0	376.2	408.5	445.7	494.7	556.4
132.5°	315.4	319.4	329.2	343.9	364.4	377.2	389.9	421.3	457.5	500.6	555.5
135°	327.2	331.1	341.9	356.6	377.2	390.4	403.6	434.0	467.3	506.5	554.5
137.5°	338.0	341.9	352.7	368.4	388.9	401.2	413.4	442.8	475.1	510.4	552.5
140°	348.8	353.7	363.5	379.1	398.7	411.0	423.2	451.6	481.0	514.3	551.5
142.5°	360.5	364.4	375.2	388.9	408.5	419.8	431.0	458.5	486.9	517.3	549.6
145°	373.2	376.2	385.0	399.7	416.4	427.6	438.9	464.4	490.8	518.2	547.6
147.5°	386.0	387.9	396.8	409.5	426.2	436.0	445.7	469.3	493.7	518.2	544.7
150°	398.7	399.7	407.5	420.3	434.0	442.8	451.6	474.2	494.7	518.2	540.8
152.5°	411.5	411.5	419.3	430.1	441.8	450.2	458.5	477.1	496.7	515.3	535.9
155°	424.2	424.2	430.1	439.9	450.6	457.5	464.4	481.0	496.7	513.3	530.0
157.5°	434.0	435.0	439.9	448.7	458.5	463.9	469.3	483.0	497.7	510.4	525.1
160°	445.7	445.7	449.7	457.5	464.4	469.3	474.2	485.9	497.7	508.4	519.2
162.5°	454.6	454.6	457.5	463.4	469.3	473.2	477.1	486.9	496.7	504.5	513.3
165°	463.4	462.4	464.4	469.3	473.2	476.6	480.0	487.9	494.7	500.6	507.5
167.5°	470.2	469.3	470.2	474.2	477.1	479.6	482.0	487.9	493.7	496.7	501.6
170°	476.1	474.2	475.1	478.1	480.0	481.0	482.0	486.9	490.8	492.8	495.7
172.5°	480.0	479.1	479.1	481.0	482.0	482.5	483.0	486.9	489.8	489.8	490.8
175°	483.0	482.0	481.0	483.0	483.0	483.4	483.9	485.9	487.9	486.9	486.9
177.5°	484.9	483.9	483.0	483.9	483.9	483.9	483.9	484.9	486.9	484.9	483.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	932.7	932.7	939.5	946.3	942.5	944.8	953.1	950.1	956.1	955.4	957.6
5°	1003.0	1011.4	1018.2	1032.5	1034.8	1032.5	1046.9	1050.7	1057.5	1049.2	1053.0
7.5°	1082.5	1099.9	1116.5	1137.7	1144.5	1146.0	1153.6	1164.2	1173.2	1156.6	1164.9
10°	1159.6	1186.1	1220.1	1239.0	1255.7	1261.7	1267.8	1274.6	1285.2	1295.0	1287.5
12.5°	1242.8	1281.4	1313.9	1348.0	1368.4	1366.1	1383.5	1388.1	1396.4	1398.6	1401.7
15°	1310.9	1365.4	1385.8	1436.5	1441.0	1456.1	1475.8	1493.2	1495.5	1490.9	1490.9
17.5°	1376.0	1422.9	1459.2	1500.0	1508.3	1521.2	1546.2	1554.5	1557.5	1556.7	1556.7
20°	1428.9	1459.9	1521.2	1555.2	1568.8	1585.5	1602.9	1613.5	1615.7	1618.8	1614.2
22.5°	1463.7	1510.6	1560.5	1588.5	1599.9	1605.9	1617.3	1620.3	1616.5	1617.3	1618.0
25°	1490.9	1537.1	1567.3	1574.9	1574.1	1566.6	1558.3	1543.9	1542.4	1536.3	1524.2
27.5°	1498.5	1515.9	1512.1	1481.1	1450.1	1447.1	1397.1	1369.9	1338.9	1343.4	1326.0
30°	1457.6	1435.0	1381.2	1302.6	1270.1	1217.1	1161.1	1102.9	1080.2	1055.2	1101.4
32.5°	1357.8	1276.9	1181.5	1079.4	1025.0	978.1	918.3	876.0	851.7	831.3	870.7
35°	1207.3	1080.9	954.6	857.8	813.2	770.8	714.8	693.6	663.4	666.4	670.2
37.5°	1013.6	874.4	779.1	683.8	654.3	636.9	596.1	563.5	553.0	549.9	549.9
40°	832.1	717.9	633.1	558.2	535.6	521.2	488.7	473.5	462.2	459.2	462.9
42.5°	688.4	590.8	525.0	475.0	459.2	441.0	427.4	408.5	406.2	400.9	407.7
45°	577.9	493.2	444.0	407.7	394.1	387.3	372.2	360.8	356.3	355.5	360.8
47.5°	490.2	424.4	381.2	358.5	348.0	341.2	328.3	323.8	319.2	320.7	318.5
50°	411.5	362.3	334.3	313.9	307.1	300.3	292.0	287.4	285.2	285.2	284.4
52.5°	353.3	312.4	294.3	275.3	272.3	268.5	259.5	256.4	252.6	251.9	254.9
55°	302.6	274.6	256.4	245.1	242.1	234.5	230.7	226.9	224.7	223.1	223.9
57.5°	258.7	237.5	225.4	215.6	210.3	207.3	200.5	199.7	198.2	198.2	197.4
60°	222.4	207.3	192.9	186.8	183.1	179.3	178.5	174.0	171.7	173.2	172.5
62.5°	188.4	176.2	167.9	161.1	158.9	155.8	153.6	152.0	149.8	150.5	150.5
65°	157.3	147.5	141.5	135.4	134.6	131.6	130.9	129.4	129.4	128.6	130.1
67.5°	129.4	122.5	117.2	113.5	111.2	112.0	108.9	106.7	106.7	105.9	108.2
70°	102.9	99.1	93.8	89.3	86.2	86.2	82.5	81.7	81.7	81.7	80.9
72.5°	79.4	72.6	70.3	68.8	68.8	68.8	67.3	67.3	66.6	67.3	66.6
75°	59.0	58.2	56.7	56.0	56.0	55.2	54.5	54.5	54.5	54.5	54.5
77.5°	46.1	46.1	44.6	43.9	43.9	43.9	43.1	43.1	42.4	42.4	42.4
80°	34.0	34.0	32.5	32.5	32.5	31.8	31.8	31.8	32.5	31.8	31.8
82.5°	23.4	23.4	22.7	23.4	22.7	21.9	21.9	21.9	21.2	21.9	21.9
85°	13.6	13.6	12.9	12.1	12.9	12.9	12.1	12.9	12.1	12.9	12.1
87.5°	5.3	4.5	4.5	4.5	3.8	4.5	3.8	3.8	4.5	3.8	4.5
90°	23.5	24.5	25.5	26.5	27.4	28.4	27.4	28.4	29.4	28.4	29.4
92.5°	136.2	97.0	75.4	65.6	62.2	58.8	56.8	52.9	53.9	51.9	53.9
95°	471.2	352.7	239.0	187.1	169.4	151.8	133.2	124.4	117.6	113.6	117.6
97.5°	923.8	810.2	611.3	482.0	426.2	370.3	304.7	267.4	243.9	233.2	243.9
100°	1120.7	1155.0	1075.7	961.0	891.4	821.9	723.0	651.5	613.3	614.2	613.3
102.5°	1130.5	1269.6	1286.3	1231.4	1193.7	1156.0	1084.5	1031.6	1001.2	972.8	1001.2
105°	1068.8	1273.6	1371.5	1390.1	1377.4	1364.7	1319.6	1282.4	1251.0	1246.1	1251.0
107.5°	980.6	1214.8	1368.6	1445.0	1458.2	1471.4	1465.6	1447.9	1435.2	1424.4	1435.2
110°	898.3	1122.7	1302.9	1426.4	1460.7	1495.0	1522.4	1530.2	1528.3	1526.3	1528.3



TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	826.8	1031.6	1216.7	1358.8	1405.3	1451.8	1507.7	1536.1	1545.9	1546.9	1545.9
115°	772.0	953.2	1123.7	1267.7	1321.1	1374.5	1447.9	1491.0	1510.6	1515.5	1510.6
117.5°	735.7	892.5	1043.3	1175.6	1230.9	1286.3	1362.7	1410.7	1440.1	1447.0	1440.1
120°	708.3	846.4	978.7	1096.2	1145.7	1195.2	1272.6	1327.4	1350.9	1356.8	1350.9
122.5°	685.8	810.2	926.8	1033.5	1078.6	1123.7	1190.3	1238.3	1264.7	1272.6	1264.7
125°	667.1	778.8	885.6	979.7	1018.8	1058.0	1120.7	1163.8	1188.3	1195.2	1188.3
127.5°	649.5	750.4	847.4	933.6	969.8	1006.1	1062.9	1100.2	1122.7	1128.6	1122.7
130°	635.8	724.0	812.1	891.5	924.8	958.1	1010.0	1045.3	1065.9	1073.7	1065.9
132.5°	623.1	699.5	778.8	851.3	882.6	914.0	962.0	997.3	1014.9	1019.8	1014.9
135°	612.3	677.9	747.5	811.2	839.1	867.0	915.0	944.4	962.0	968.9	962.0
137.5°	602.5	657.3	716.1	772.9	797.9	822.9	864.1	894.4	909.1	915.0	909.1
140°	593.7	639.7	689.7	736.7	757.8	778.8	816.1	843.5	859.2	858.2	859.2
142.5°	585.8	623.1	664.2	703.4	721.0	738.7	769.0	792.5	806.3	805.3	806.3
145°	579.0	610.3	642.7	674.0	688.2	702.4	726.9	747.5	755.3	757.3	755.3
147.5°	572.1	599.5	626.0	652.5	662.8	673.0	692.6	707.3	715.1	716.1	715.1
150°	565.3	587.8	610.3	630.9	640.2	649.5	664.2	675.0	680.9	680.9	680.9
152.5°	557.4	577.0	595.6	613.3	620.6	628.0	638.7	648.5	651.5	651.5	651.5
155°	549.6	566.2	581.9	596.6	602.5	608.4	617.2	625.0	627.0	628.0	627.0
157.5°	540.8	554.5	568.2	580.0	584.9	589.8	597.6	603.5	605.4	605.4	605.4
160°	532.0	544.7	555.5	565.3	568.7	572.1	579.0	584.9	584.9	583.9	584.9
162.5°	523.1	532.9	541.7	550.6	553.5	556.4	560.4	565.3	565.3	564.3	565.3
165°	515.3	523.1	529.0	535.9	538.3	540.8	544.7	548.6	547.6	547.6	547.6
167.5°	507.5	514.3	519.2	523.1	525.1	527.1	529.0	532.0	531.0	531.0	531.0
170°	500.6	505.5	508.4	512.4	513.3	514.3	515.3	517.3	516.3	516.3	516.3
172.5°	493.7	497.7	499.6	502.6	503.0	503.5	503.5	505.5	503.5	502.6	503.5
175°	488.8	490.8	491.8	493.7	493.7	493.7	493.7	494.7	493.7	492.8	493.7
177.5°	484.9	485.9	486.9	487.9	487.9	487.9	486.9	487.9	485.9	485.9	485.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	953.9	949.3	946.3	944.0	941.8	948.6	939.5	929.7	922.8	918.3	916.8
5°	1053.7	1043.9	1035.6	1028.7	1030.3	1030.3	1014.4	997.0	981.9	973.5	964.5
7.5°	1169.4	1158.9	1142.2	1138.4	1135.4	1116.5	1100.6	1068.8	1049.9	1031.0	1014.4
10°	1284.4	1270.8	1254.9	1249.6	1242.1	1218.6	1194.4	1153.6	1130.1	1095.3	1073.4
12.5°	1391.8	1375.2	1359.3	1355.5	1344.2	1323.8	1282.2	1239.8	1199.7	1162.6	1124.1
15°	1481.9	1477.3	1453.1	1438.0	1413.0	1385.0	1376.0	1318.5	1267.8	1229.2	1159.6
17.5°	1557.5	1536.3	1513.6	1503.8	1494.0	1461.4	1428.9	1369.9	1315.4	1258.7	1214.1
20°	1618.0	1594.6	1578.7	1564.3	1559.8	1522.7	1471.3	1419.1	1359.3	1295.8	1237.5
22.5°	1621.0	1618.0	1607.4	1599.1	1590.0	1565.8	1525.0	1459.9	1396.4	1326.8	1250.4
25°	1558.3	1553.7	1584.0	1576.4	1582.5	1573.4	1551.4	1497.0	1422.9	1341.2	1264.0
27.5°	1369.1	1415.3	1462.9	1479.6	1490.9	1523.5	1534.0	1503.8	1444.0	1357.0	1270.8
30°	1112.0	1173.2	1250.4	1292.0	1323.8	1384.3	1462.9	1472.8	1444.8	1375.2	1269.3
32.5°	872.9	928.9	990.9	1040.1	1082.5	1206.5	1312.4	1388.8	1402.4	1366.1	1273.1
35°	703.5	727.7	786.7	833.6	891.1	997.0	1121.8	1245.1	1328.3	1332.8	1261.7
37.5°	580.2	593.0	644.5	671.0	705.0	798.0	914.5	1075.6	1205.0	1266.3	1230.0
40°	480.3	509.8	539.3	554.5	578.7	643.0	754.9	881.2	1041.6	1155.1	1180.8
42.5°	416.8	429.7	448.6	469.7	484.9	540.9	615.7	731.5	876.0	1034.0	1105.1
45°	367.6	372.2	391.8	405.4	421.3	460.7	513.6	610.4	737.5	893.3	1014.4
47.5°	326.8	335.9	346.4	354.8	365.4	395.6	441.0	511.3	623.3	762.5	892.6
50°	290.5	295.8	309.4	313.2	320.7	341.9	376.7	430.4	522.7	633.9	768.5
52.5°	256.4	266.3	271.6	276.9	283.7	301.1	323.8	367.6	437.2	541.6	655.8
55°	230.0	233.0	240.5	245.1	250.4	262.5	282.1	314.7	369.1	452.3	560.5
57.5°	204.2	204.2	211.8	215.6	220.9	230.0	247.4	272.3	311.7	373.7	472.8
60°	177.0	177.8	183.8	188.4	189.9	198.9	213.3	233.0	263.2	308.6	389.6
62.5°	152.8	156.6	159.6	161.1	166.4	171.7	183.8	197.4	218.6	258.7	316.2
65°	132.4	133.1	135.4	136.9	139.2	145.2	154.3	163.4	181.5	211.0	257.9
67.5°	108.9	112.0	115.0	115.0	117.2	120.3	129.4	136.9	150.5	167.9	199.7
70°	81.7	83.2	87.7	90.0	93.0	98.3	102.9	107.4	118.0	130.9	155.1
72.5°	68.1	68.1	69.6	70.3	70.3	74.1	80.9	85.5	90.8	99.8	116.5
75°	54.5	54.5	56.7	56.0	57.5	59.0	59.8	62.8	65.8	72.6	82.5
77.5°	43.1	43.9	43.9	44.6	44.6	45.4	46.1	47.7	49.2	53.0	57.5
80°	31.8	32.5	32.5	33.3	33.3	34.0	34.8	35.6	37.1	38.6	40.8
82.5°	21.9	22.7	22.7	23.4	22.7	23.4	24.2	24.2	25.0	26.5	27.2
85°	12.9	12.9	13.6	12.9	12.9	12.9	13.6	13.6	14.4	16.6	16.6
87.5°	3.8	4.5	3.8	4.5	4.5	4.5	4.5	5.3	5.3	6.1	6.8
90°	28.4	27.4	28.4	27.4	26.5	25.5	24.5	23.5	24.5	21.6	18.6
92.5°	52.9	56.8	58.8	62.2	65.6	75.4	97.0	136.2	182.2	201.8	150.9
95°	124.4	133.2	151.8	169.4	187.1	239.0	352.7	471.2	580.9	517.3	356.6
97.5°	267.4	304.7	370.3	426.2	482.0	611.3	810.2	923.8	893.4	667.1	396.8
100°	651.5	723.0	821.9	891.4	961.0	1075.7	1155.0	1120.7	927.7	627.0	369.3
102.5°	1031.6	1084.5	1156.0	1193.7	1231.4	1286.3	1269.6	1130.5	864.1	568.2	345.8
105°	1282.4	1319.6	1364.7	1377.4	1390.1	1371.5	1273.6	1068.8	787.6	522.2	337.0
107.5°	1447.9	1465.6	1471.4	1458.2	1445.0	1368.6	1214.8	980.6	720.0	488.8	335.0
110°	1530.2	1522.4	1495.0	1460.7	1426.4	1302.9	1122.7	898.3	664.2	471.2	339.9

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1536.1	1507.7	1451.8	1405.3	1358.8	1216.7	1031.6	826.8	627.0	461.4	349.7
115°	1491.0	1447.9	1374.5	1321.1	1267.7	1123.7	953.2	772.0	602.5	460.4	360.5
117.5°	1410.7	1362.7	1286.3	1230.9	1175.6	1043.3	892.5	735.7	585.8	461.4	374.2
120°	1327.4	1272.6	1195.2	1145.7	1096.2	978.7	846.4	708.3	575.1	465.3	389.9
122.5°	1238.3	1190.3	1123.7	1078.6	1033.5	926.8	810.2	685.8	568.2	472.2	404.6
125°	1163.8	1120.7	1058.0	1018.8	979.7	885.6	778.8	667.1	562.3	479.1	420.3
127.5°	1100.2	1062.9	1006.1	969.8	933.6	847.4	750.4	649.5	559.4	486.9	433.0
130°	1045.3	1010.0	958.1	924.8	891.5	812.1	724.0	635.8	556.4	494.7	445.7
132.5°	997.3	962.0	914.0	882.6	851.3	778.8	699.5	623.1	555.5	500.6	457.5
135°	944.4	915.0	867.0	839.1	811.2	747.5	677.9	612.3	554.5	506.5	467.3
137.5°	894.4	864.1	822.9	797.9	772.9	716.1	657.3	602.5	552.5	510.4	475.1
140°	843.5	816.1	778.8	757.8	736.7	689.7	639.7	593.7	551.5	514.3	481.0
142.5°	792.5	769.0	738.7	721.0	703.4	664.2	623.1	585.8	549.6	517.3	486.9
145°	747.5	726.9	702.4	688.2	674.0	642.7	610.3	579.0	547.6	518.2	490.8
147.5°	707.3	692.6	673.0	662.8	652.5	626.0	599.5	572.1	544.7	518.2	493.7
150°	675.0	664.2	649.5	640.2	630.9	610.3	587.8	565.3	540.8	518.2	494.7
152.5°	648.5	638.7	628.0	620.6	613.3	595.6	577.0	557.4	535.9	515.3	496.7
155°	625.0	617.2	608.4	602.5	596.6	581.9	566.2	549.6	530.0	513.3	496.7
157.5°	603.5	597.6	589.8	584.9	580.0	568.2	554.5	540.8	525.1	510.4	497.7
160°	584.9	579.0	572.1	568.7	565.3	555.5	544.7	532.0	519.2	508.4	497.7
162.5°	565.3	560.4	556.4	553.5	550.6	541.7	532.9	523.1	513.3	504.5	496.7
165°	548.6	544.7	540.8	538.3	535.9	529.0	523.1	515.3	507.5	500.6	494.7
167.5°	532.0	529.0	527.1	525.1	523.1	519.2	514.3	507.5	501.6	496.7	493.7
170°	517.3	515.3	514.3	513.3	512.4	508.4	505.5	500.6	495.7	492.8	490.8
172.5°	505.5	503.5	503.5	503.0	502.6	499.6	497.7	493.7	490.8	489.8	489.8
175°	494.7	493.7	493.7	493.7	493.7	491.8	490.8	488.8	486.9	486.9	487.9
177.5°	487.9	486.9	487.9	487.9	487.9	486.9	485.9	484.9	483.9	484.9	486.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	914.5	910.7	907.0	907.0	898.6	891.1	887.3	888.8	884.3	878.2	872.2
5°	954.6	939.5	936.5	928.1	916.8	900.9	892.6	885.0	876.0	863.8	852.5
7.5°	991.7	972.0	961.4	953.1	931.2	909.2	891.1	879.0	863.1	844.9	831.3
10°	1040.1	1003.8	992.4	973.5	942.5	911.5	890.3	870.7	848.7	827.5	809.4
12.5°	1078.7	1037.1	1015.9	997.0	956.9	917.6	882.0	857.8	831.3	807.9	784.4
15°	1122.5	1075.6	1038.6	1015.9	965.2	917.6	877.5	843.4	813.9	785.2	764.8
17.5°	1143.7	1084.7	1068.1	1035.6	962.2	914.5	865.4	829.1	793.5	760.2	736.0
20°	1177.0	1108.2	1066.6	1044.6	979.6	909.2	851.7	810.1	773.1	737.5	711.8
22.5°	1179.3	1104.4	1077.2	1035.6	955.4	893.3	839.6	789.0	745.8	712.6	686.1
25°	1174.0	1097.6	1059.8	1026.5	959.9	884.3	815.4	765.5	723.2	684.6	653.6
27.5°	1171.7	1077.9	1042.4	1009.1	934.2	857.8	801.1	744.3	695.9	661.9	630.1
30°	1168.7	1056.7	1013.6	975.0	906.2	837.4	769.3	720.1	674.0	630.9	599.1
32.5°	1149.0	1028.0	984.1	943.3	869.1	800.3	746.6	694.4	644.5	604.4	575.6
35°	1143.0	1001.5	944.0	900.2	827.5	766.3	709.5	666.4	619.5	579.4	545.4
37.5°	1125.6	974.3	912.3	856.3	780.6	722.4	680.8	637.7	592.3	549.2	521.9
40°	1095.3	942.5	872.2	814.7	736.8	677.8	639.2	607.4	562.8	524.2	490.9
42.5°	1050.7	910.0	834.3	773.8	687.6	632.4	600.6	570.4	532.5	492.4	465.2
45°	999.2	866.9	796.5	729.2	641.5	587.7	554.5	536.3	501.5	467.5	435.7
47.5°	928.9	822.2	752.7	683.1	593.8	541.6	515.1	497.0	472.8	435.7	410.0
50°	840.4	764.8	698.9	636.9	546.9	497.0	470.5	456.9	436.5	410.0	385.0
52.5°	742.1	698.2	643.7	586.2	499.2	452.3	428.1	417.6	402.4	377.5	356.3
55°	643.0	624.1	587.0	530.3	449.3	410.7	389.6	375.9	364.6	346.4	328.3
57.5°	554.5	545.4	519.7	475.8	407.7	367.6	349.5	340.4	331.3	317.7	299.5
60°	462.9	472.8	446.3	424.4	362.3	327.5	311.7	301.8	297.3	285.2	273.8
62.5°	383.5	392.6	377.5	360.8	316.9	285.9	276.1	267.0	264.0	253.4	242.1
65°	311.7	323.0	311.7	302.6	276.1	250.4	238.3	233.7	230.7	223.9	214.8
67.5°	248.1	259.5	254.2	242.8	234.5	213.3	206.5	202.0	200.5	195.2	187.6
70°	186.8	202.7	204.2	197.4	189.9	180.0	175.5	174.0	170.2	165.7	161.1
72.5°	134.6	152.8	153.6	153.6	149.0	149.0	144.5	142.2	142.2	137.7	132.4
75°	99.1	111.2	112.7	114.2	116.5	118.8	115.7	115.7	115.0	110.4	108.2
77.5°	65.8	76.4	80.2	85.5	88.5	88.5	90.0	91.5	90.0	87.7	86.2
80°	42.4	49.9	54.5	57.5	62.0	64.3	66.6	67.3	65.8	65.1	62.8
82.5°	28.0	30.3	32.5	36.3	41.6	45.4	45.4	44.6	46.1	45.4	44.6
85°	15.9	17.4	18.2	18.9	21.9	25.7	26.5	27.2	28.7	27.2	25.7
87.5°	6.1	6.8	6.8	6.8	8.3	9.1	11.3	14.4	13.6	12.1	12.1
90°	15.7	12.7	11.8	10.8	8.8	5.9	3.9	2.0	3.9	5.9	8.8
92.5°	98.9	67.6	58.8	50.0	40.2	31.3	21.6	14.7	21.6	31.3	40.2
95°	210.6	127.4	108.2	89.1	63.7	47.0	36.2	33.3	36.2	47.0	63.7
97.5°	227.3	145.0	124.0	102.9	77.4	62.7	53.9	52.9	53.9	62.7	77.4
100°	224.3	155.8	136.7	117.6	94.0	80.3	73.5	72.5	73.5	80.3	94.0
102.5°	228.3	168.5	151.4	134.2	113.6	100.9	95.0	93.1	95.0	100.9	113.6
105°	236.1	183.2	168.0	152.8	134.2	122.5	116.6	113.6	116.6	122.5	134.2
107.5°	248.8	201.8	187.6	173.4	155.8	144.0	138.1	135.2	138.1	144.0	155.8
110°	265.5	221.4	207.7	194.0	177.3	166.5	161.6	158.7	161.6	166.5	177.3

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	282.1	242.0	228.8	215.5	198.9	188.1	183.2	180.3	183.2	188.1	198.9
115°	300.8	263.5	250.3	237.1	220.4	210.6	204.7	200.8	204.7	210.6	220.4
117.5°	320.3	283.1	270.8	258.6	240.0	231.2	226.3	221.4	226.3	231.2	240.0
120°	339.0	303.7	291.4	279.2	260.6	250.8	245.9	243.0	245.9	250.8	260.6
122.5°	358.6	324.3	311.0	297.8	280.2	269.4	264.5	261.6	264.5	269.4	280.2
125°	377.2	342.9	329.6	316.4	297.8	287.0	281.2	279.2	281.2	287.0	297.8
127.5°	393.8	360.5	347.3	334.1	313.5	302.7	295.9	292.9	295.9	302.7	313.5
130°	408.5	376.2	363.0	349.7	329.2	317.4	308.6	305.7	308.6	317.4	329.2
132.5°	421.3	389.9	377.2	364.4	343.9	329.2	319.4	315.4	319.4	329.2	343.9
135°	434.0	403.6	390.4	377.2	356.6	341.9	331.1	327.2	331.1	341.9	356.6
137.5°	442.8	413.4	401.2	388.9	368.4	352.7	341.9	338.0	341.9	352.7	368.4
140°	451.6	423.2	411.0	398.7	379.1	363.5	353.7	348.8	353.7	363.5	379.1
142.5°	458.5	431.0	419.8	408.5	388.9	375.2	364.4	360.5	364.4	375.2	388.9
145°	464.4	438.9	427.6	416.4	399.7	385.0	376.2	373.2	376.2	385.0	399.7
147.5°	469.3	445.7	436.0	426.2	409.5	396.8	387.9	386.0	387.9	396.8	409.5
150°	474.2	451.6	442.8	434.0	420.3	407.5	399.7	398.7	399.7	407.5	420.3
152.5°	477.1	458.5	450.2	441.8	430.1	419.3	411.5	411.5	411.5	419.3	430.1
155°	481.0	464.4	457.5	450.6	439.9	430.1	424.2	424.2	424.2	430.1	439.9
157.5°	483.0	469.3	463.9	458.5	448.7	439.9	435.0	434.0	435.0	439.9	448.7
160°	485.9	474.2	469.3	464.4	457.5	449.7	445.7	445.7	445.7	449.7	457.5
162.5°	486.9	477.1	473.2	469.3	463.4	457.5	454.6	454.6	454.6	457.5	463.4
165°	487.9	480.0	476.6	473.2	469.3	464.4	462.4	463.4	462.4	464.4	469.3
167.5°	487.9	482.0	479.6	477.1	474.2	470.2	469.3	470.2	469.3	470.2	474.2
170°	486.9	482.0	481.0	480.0	478.1	475.1	474.2	476.1	474.2	475.1	478.1
172.5°	486.9	483.0	482.5	482.0	481.0	479.1	479.1	480.0	479.1	479.1	481.0
175°	485.9	483.9	483.4	483.0	483.0	481.0	482.0	483.0	482.0	481.0	483.0
177.5°	484.9	483.9	483.9	483.9	483.9	483.0	483.9	484.9	483.9	483.0	483.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	872.2	868.4	866.9	863.1	854.0	848.0	841.2	836.6	837.4	833.6	835.9
5°	844.9	844.2	838.9	831.3	818.5	811.7	799.6	793.5	790.5	791.2	786.7
7.5°	822.2	815.4	811.7	799.6	787.4	773.1	763.2	757.9	753.4	748.9	745.8
10°	796.5	790.5	784.4	771.6	754.9	741.3	727.7	722.4	715.6	712.6	710.3
12.5°	769.3	765.5	757.9	742.8	723.9	711.0	695.2	692.1	683.1	677.0	675.5
15°	744.3	742.1	728.4	711.0	692.1	679.3	665.7	656.6	641.5	644.5	639.2
17.5°	717.9	708.0	699.7	676.3	667.2	647.5	631.6	627.1	616.5	609.7	602.9
20°	688.4	682.3	671.7	656.6	634.6	612.0	599.9	592.3	586.2	575.6	572.6
22.5°	660.4	652.8	643.7	624.1	605.1	586.2	569.6	562.8	555.2	547.7	543.1
25°	638.4	627.1	617.2	593.0	574.1	558.2	547.7	536.3	525.7	521.2	519.7
27.5°	604.4	597.6	587.7	565.1	547.7	530.3	520.4	512.9	501.5	496.2	491.7
30°	582.5	568.8	557.5	539.3	521.9	503.0	494.0	484.9	478.1	471.3	466.0
32.5°	553.0	542.4	533.3	515.1	497.7	480.3	470.5	456.9	453.1	447.8	441.8
35°	524.2	517.4	507.6	487.9	469.0	456.9	446.3	433.4	428.9	425.1	419.8
37.5°	497.0	487.1	480.3	461.4	444.8	430.4	422.1	411.5	408.5	403.9	400.2
40°	473.5	463.7	456.9	438.0	420.6	405.4	400.2	389.6	385.0	379.7	377.5
42.5°	447.1	438.7	429.7	416.0	397.9	382.8	372.2	366.1	360.1	357.8	353.3
45°	419.1	411.5	404.7	389.6	370.7	360.1	351.0	342.7	338.1	334.3	331.3
47.5°	394.9	388.1	379.0	362.3	347.2	337.4	328.3	320.0	315.4	310.9	307.1
50°	366.9	363.1	353.3	337.4	323.0	311.7	303.3	295.8	292.7	287.4	281.4
52.5°	341.9	335.1	326.8	313.9	301.1	287.4	276.1	271.6	266.3	263.2	257.9
55°	312.4	307.9	298.8	287.4	273.8	262.5	254.2	248.1	241.3	238.3	231.5
57.5°	287.4	279.1	274.6	260.2	247.4	236.0	230.0	223.9	216.3	211.8	208.8
60°	260.2	252.6	245.8	233.7	224.7	212.6	203.5	198.2	192.9	186.8	183.8
62.5°	233.7	227.7	219.4	209.5	198.2	188.4	181.5	174.0	171.0	164.9	162.6
65°	205.0	200.5	193.6	182.3	173.2	164.9	158.1	152.0	149.0	146.7	145.2
67.5°	179.3	173.2	168.7	158.9	149.0	142.2	138.4	134.6	130.9	128.6	126.3
70°	152.8	148.3	143.7	134.6	127.8	121.8	118.8	115.7	113.5	111.2	108.9
72.5°	125.6	123.3	118.8	112.7	107.4	102.9	100.6	96.8	94.6	90.8	89.3
75°	103.6	99.8	97.6	92.3	87.7	84.0	80.9	76.4	73.4	71.9	71.1
77.5°	81.7	80.2	77.2	72.6	70.3	66.6	62.0	60.5	59.0	59.0	58.2
80°	61.3	59.0	56.7	53.0	50.7	47.7	47.7	47.7	46.9	47.7	46.9
82.5°	41.6	40.1	38.6	36.3	35.6	35.6	36.3	36.3	36.3	36.3	36.3
85°	24.2	24.2	24.2	25.0	24.2	24.2	25.0	25.7	25.0	25.0	24.2
87.5°	11.3	11.3	12.1	12.1	12.9	12.9	12.9	12.9	12.9	12.9	13.6
90°	10.8	11.8	12.7	15.7	18.6	21.6	24.5	23.5	24.5	25.5	26.5
92.5°	50.0	58.8	67.6	98.9	150.9	201.8	182.2	136.2	97.0	75.4	65.6
95°	89.1	108.2	127.4	210.6	356.6	517.3	580.9	471.2	352.7	239.0	187.1
97.5°	102.9	124.0	145.0	227.3	396.8	667.1	893.4	923.8	810.2	611.3	482.0
100°	117.6	136.7	155.8	224.3	369.3	627.0	927.7	1120.7	1155.0	1075.7	961.0
102.5°	134.2	151.4	168.5	228.3	345.8	568.2	864.1	1130.5	1269.6	1286.3	1231.4
105°	152.8	168.0	183.2	236.1	337.0	522.2	787.6	1068.8	1273.6	1371.5	1390.1
107.5°	173.4	187.6	201.8	248.8	335.0	488.8	720.0	980.6	1214.8	1368.6	1445.0
110°	194.0	207.7	221.4	265.5	339.9	471.2	664.2	898.3	1122.7	1302.9	1426.4

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	215.5	228.8	242.0	282.1	349.7	461.4	627.0	826.8	1031.6	1216.7	1358.8
115°	237.1	250.3	263.5	300.8	360.5	460.4	602.5	772.0	953.2	1123.7	1267.7
117.5°	258.6	270.8	283.1	320.3	374.2	461.4	585.8	735.7	892.5	1043.3	1175.6
120°	279.2	291.4	303.7	339.0	389.9	465.3	575.1	708.3	846.4	978.7	1096.2
122.5°	297.8	311.0	324.3	358.6	404.6	472.2	568.2	685.8	810.2	926.8	1033.5
125°	316.4	329.6	342.9	377.2	420.3	479.1	562.3	667.1	778.8	885.6	979.7
127.5°	334.1	347.3	360.5	393.8	433.0	486.9	559.4	649.5	750.4	847.4	933.6
130°	349.7	363.0	376.2	408.5	445.7	494.7	556.4	635.8	724.0	812.1	891.5
132.5°	364.4	377.2	389.9	421.3	457.5	500.6	555.5	623.1	699.5	778.8	851.3
135°	377.2	390.4	403.6	434.0	467.3	506.5	554.5	612.3	677.9	747.5	811.2
137.5°	388.9	401.2	413.4	442.8	475.1	510.4	552.5	602.5	657.3	716.1	772.9
140°	398.7	411.0	423.2	451.6	481.0	514.3	551.5	593.7	639.7	689.7	736.7
142.5°	408.5	419.8	431.0	458.5	486.9	517.3	549.6	585.8	623.1	664.2	703.4
145°	416.4	427.6	438.9	464.4	490.8	518.2	547.6	579.0	610.3	642.7	674.0
147.5°	426.2	436.0	445.7	469.3	493.7	518.2	544.7	572.1	599.5	626.0	652.5
150°	434.0	442.8	451.6	474.2	494.7	518.2	540.8	565.3	587.8	610.3	630.9
152.5°	441.8	450.2	458.5	477.1	496.7	515.3	535.9	557.4	577.0	595.6	613.3
155°	450.6	457.5	464.4	481.0	496.7	513.3	530.0	549.6	566.2	581.9	596.6
157.5°	458.5	463.9	469.3	483.0	497.7	510.4	525.1	540.8	554.5	568.2	580.0
160°	464.4	469.3	474.2	485.9	497.7	508.4	519.2	532.0	544.7	555.5	565.3
162.5°	469.3	473.2	477.1	486.9	496.7	504.5	513.3	523.1	532.9	541.7	550.6
165°	473.2	476.6	480.0	487.9	494.7	500.6	507.5	515.3	523.1	529.0	535.9
167.5°	477.1	479.6	482.0	487.9	493.7	496.7	501.6	507.5	514.3	519.2	523.1
170°	480.0	481.0	482.0	486.9	490.8	492.8	495.7	500.6	505.5	508.4	512.4
172.5°	482.0	482.5	483.0	486.9	489.8	489.8	490.8	493.7	497.7	499.6	502.6
175°	483.0	483.4	483.9	485.9	487.9	486.9	486.9	488.8	490.8	491.8	493.7
177.5°	483.9	483.9	483.9	484.9	486.9	484.9	483.9	484.9	485.9	486.9	487.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.1	835.9	833.6	829.1	828.3	829.8	834.3	832.8	829.1	835.9	829.8
5°	789.0	785.2	783.7	785.2	780.6	778.4	782.9	780.6	782.9	783.7	785.9
7.5°	744.3	745.1	740.5	741.3	735.3	736.8	736.8	736.8	739.0	740.5	743.6
10°	705.8	707.3	702.0	702.7	698.2	695.2	697.4	702.0	702.0	702.0	703.5
12.5°	674.7	667.9	664.1	663.4	658.1	656.6	661.1	662.6	666.4	666.4	668.7
15°	636.2	634.6	631.6	631.6	618.8	621.8	623.3	628.6	636.2	630.1	631.6
17.5°	601.4	597.6	593.8	592.3	590.8	586.2	592.3	591.5	596.1	596.8	599.1
20°	570.4	567.3	559.8	560.5	562.0	555.2	559.0	559.0	563.5	568.1	573.4
22.5°	540.1	537.1	533.3	534.8	530.3	528.7	528.7	532.5	537.8	541.6	540.9
25°	516.6	511.3	509.1	506.8	504.5	506.1	503.8	507.6	511.3	513.6	511.3
27.5°	490.2	487.9	483.4	481.1	477.3	478.8	480.3	483.4	485.6	485.6	487.9
30°	464.5	461.4	459.9	457.6	457.6	454.6	455.4	458.4	460.7	462.9	466.0
32.5°	439.5	437.2	434.9	434.9	433.4	432.7	431.9	436.5	436.5	441.0	441.0
35°	419.1	415.3	415.3	411.5	413.0	412.3	410.7	413.8	414.5	417.6	416.8
37.5°	396.4	396.4	394.9	391.1	388.1	388.8	392.6	392.6	394.9	394.1	396.4
40°	373.7	372.2	372.2	369.9	369.1	368.4	369.1	369.9	373.7	372.9	373.7
42.5°	351.0	351.7	348.0	348.0	348.0	345.7	346.4	347.2	348.7	350.2	352.5
45°	329.0	327.5	326.8	325.3	323.8	324.5	323.8	326.8	326.0	327.5	329.8
47.5°	305.6	303.3	302.6	299.5	299.5	301.1	300.3	302.6	303.3	305.6	304.1
50°	282.9	279.9	277.6	278.4	273.8	275.3	275.3	277.6	279.9	280.6	282.1
52.5°	256.4	255.7	254.9	251.1	250.4	249.6	250.4	251.1	254.2	256.4	257.2
55°	230.7	230.0	225.4	223.9	221.6	221.6	223.1	223.9	229.2	230.0	233.0
57.5°	207.3	205.0	199.7	198.9	198.9	198.9	196.7	199.7	201.2	205.0	205.0
60°	181.5	181.5	177.0	177.0	177.8	177.0	177.0	177.8	177.8	180.8	182.3
62.5°	161.1	160.4	160.4	158.9	158.1	158.9	158.1	158.1	158.9	161.1	163.4
65°	143.0	142.2	141.5	140.7	139.2	139.2	139.9	141.5	141.5	143.0	143.7
67.5°	125.6	125.6	124.1	124.1	123.3	122.5	123.3	122.5	125.6	125.6	126.3
70°	108.2	107.4	105.1	104.4	102.1	102.9	102.9	105.1	105.9	107.4	108.9
72.5°	87.0	87.0	85.5	84.0	84.7	83.2	83.2	84.0	84.0	86.2	87.0
75°	71.9	70.3	69.6	70.3	69.6	71.1	69.6	69.6	71.1	71.1	71.1
77.5°	59.0	59.0	58.2	58.2	59.0	58.2	59.0	59.0	59.0	58.2	59.0
80°	48.4	47.7	47.7	47.7	46.9	46.9	46.9	46.9	46.9	46.9	46.9
82.5°	36.3	36.3	35.6	36.3	36.3	35.6	36.3	35.6	35.6	36.3	36.3
85°	24.2	25.7	24.2	24.2	25.0	25.0	25.7	25.0	25.7	24.2	25.0
87.5°	12.9	13.6	13.6	12.9	12.9	13.6	13.6	13.6	14.4	12.9	13.6
90°	27.4	28.4	27.4	28.4	29.4	28.4	29.4	28.4	27.4	28.4	27.4
92.5°	62.2	58.8	56.8	52.9	53.9	51.9	53.9	52.9	56.8	58.8	62.2
95°	169.4	151.8	133.2	124.4	117.6	113.6	117.6	124.4	133.2	151.8	169.4
97.5°	426.2	370.3	304.7	267.4	243.9	233.2	243.9	267.4	304.7	370.3	426.2
100°	891.4	821.9	723.0	651.5	613.3	614.2	613.3	651.5	723.0	821.9	891.4
102.5°	1193.7	1156.0	1084.5	1031.6	1001.2	972.8	1001.2	1031.6	1084.5	1156.0	1193.7
105°	1377.4	1364.7	1319.6	1282.4	1251.0	1246.1	1251.0	1282.4	1319.6	1364.7	1377.4
107.5°	1458.2	1471.4	1465.6	1447.9	1435.2	1424.4	1435.2	1447.9	1465.6	1471.4	1458.2
110°	1460.7	1495.0	1522.4	1530.2	1528.3	1526.3	1528.3	1530.2	1522.4	1495.0	1460.7

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1405.3	1451.8	1507.7	1536.1	1545.9	1546.9	1545.9	1536.1	1507.7	1451.8	1405.3
115°	1321.1	1374.5	1447.9	1491.0	1510.6	1515.5	1510.6	1491.0	1447.9	1374.5	1321.1
117.5°	1230.9	1286.3	1362.7	1410.7	1440.1	1447.0	1440.1	1410.7	1362.7	1286.3	1230.9
120°	1145.7	1195.2	1272.6	1327.4	1350.9	1356.8	1350.9	1327.4	1272.6	1195.2	1145.7
122.5°	1078.6	1123.7	1190.3	1238.3	1264.7	1272.6	1264.7	1238.3	1190.3	1123.7	1078.6
125°	1018.8	1058.0	1120.7	1163.8	1188.3	1195.2	1188.3	1163.8	1120.7	1058.0	1018.8
127.5°	969.8	1006.1	1062.9	1100.2	1122.7	1128.6	1122.7	1100.2	1062.9	1006.1	969.8
130°	924.8	958.1	1010.0	1045.3	1065.9	1073.7	1065.9	1045.3	1010.0	958.1	924.8
132.5°	882.6	914.0	962.0	997.3	1014.9	1019.8	1014.9	997.3	962.0	914.0	882.6
135°	839.1	867.0	915.0	944.4	962.0	968.9	962.0	944.4	915.0	867.0	839.1
137.5°	797.9	822.9	864.1	894.4	909.1	915.0	909.1	894.4	864.1	822.9	797.9
140°	757.8	778.8	816.1	843.5	859.2	858.2	859.2	843.5	816.1	778.8	757.8
142.5°	721.0	738.7	769.0	792.5	806.3	805.3	806.3	792.5	769.0	738.7	721.0
145°	688.2	702.4	726.9	747.5	755.3	757.3	755.3	747.5	726.9	702.4	688.2
147.5°	662.8	673.0	692.6	707.3	715.1	716.1	715.1	707.3	692.6	673.0	662.8
150°	640.2	649.5	664.2	675.0	680.9	680.9	680.9	675.0	664.2	649.5	640.2
152.5°	620.6	628.0	638.7	648.5	651.5	651.5	651.5	648.5	638.7	628.0	620.6
155°	602.5	608.4	617.2	625.0	627.0	628.0	627.0	625.0	617.2	608.4	602.5
157.5°	584.9	589.8	597.6	603.5	605.4	605.4	605.4	603.5	597.6	589.8	584.9
160°	568.7	572.1	579.0	584.9	584.9	583.9	584.9	584.9	579.0	572.1	568.7
162.5°	553.5	556.4	560.4	565.3	565.3	564.3	565.3	565.3	560.4	556.4	553.5
165°	538.3	540.8	544.7	548.6	547.6	547.6	547.6	548.6	544.7	540.8	538.3
167.5°	525.1	527.1	529.0	532.0	531.0	531.0	531.0	532.0	529.0	527.1	525.1
170°	513.3	514.3	515.3	517.3	516.3	516.3	516.3	517.3	515.3	514.3	513.3
172.5°	503.0	503.5	503.5	505.5	503.5	502.6	503.5	505.5	503.5	503.5	503.0
175°	493.7	493.7	493.7	494.7	493.7	492.8	493.7	494.7	493.7	493.7	493.7
177.5°	487.9	487.9	486.9	487.9	485.9	485.9	485.9	487.9	486.9	487.9	487.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.9	838.9	835.9	829.8	835.9	839.6	843.4	849.5	852.5	852.5	857.0
5°	788.2	794.3	792.0	790.5	796.5	800.3	806.4	813.9	822.2	827.5	833.6
7.5°	745.8	749.6	753.4	753.4	759.5	767.8	776.9	785.9	796.5	804.1	808.6
10°	708.8	711.8	714.1	717.1	726.2	735.3	747.4	758.7	767.8	776.1	783.7
12.5°	673.2	677.8	683.1	685.3	692.1	703.5	714.8	728.4	742.8	751.1	758.7
15°	639.2	641.5	647.5	654.3	660.4	672.5	686.8	701.2	713.3	726.2	733.0
17.5°	604.4	605.1	621.0	617.2	636.9	648.3	655.8	669.4	689.1	699.7	710.3
20°	570.4	577.9	584.7	588.5	599.1	612.0	633.9	644.5	660.4	670.2	679.3
22.5°	543.9	555.2	555.2	564.3	569.6	581.7	597.6	618.0	635.4	642.2	655.1
25°	520.4	525.7	534.8	537.8	547.7	558.2	568.8	590.8	609.7	618.8	627.8
27.5°	490.2	497.0	509.1	509.1	521.9	533.3	546.1	560.5	579.4	592.3	602.1
30°	466.7	473.5	478.8	487.1	492.4	503.0	525.7	536.3	553.0	564.3	576.4
32.5°	444.8	450.1	454.6	463.7	469.7	481.8	494.0	512.9	527.2	537.8	550.7
35°	420.6	425.9	431.9	438.7	447.8	459.2	470.5	486.4	500.8	510.6	521.2
37.5°	397.9	401.7	410.7	415.3	422.8	433.4	447.8	464.5	477.3	484.9	495.5
40°	375.9	379.0	385.8	394.1	399.4	407.7	422.8	437.2	453.1	462.2	470.5
42.5°	352.5	356.3	362.3	370.7	379.0	388.1	396.4	413.0	427.4	434.9	444.0
45°	332.1	334.3	338.9	347.2	355.5	362.3	375.2	390.3	403.9	410.0	419.8
47.5°	307.9	310.1	316.9	320.7	329.8	338.9	351.7	366.9	379.0	385.0	394.1
50°	282.9	285.2	289.7	298.0	304.1	313.9	325.3	338.1	353.3	361.6	366.9
52.5°	258.7	263.2	267.0	273.8	281.4	291.2	301.8	313.9	326.8	335.1	341.2
55°	234.5	238.3	242.8	246.6	255.7	264.8	276.9	288.2	299.5	307.1	313.9
57.5°	207.3	212.6	217.1	224.7	231.5	239.0	252.6	261.7	275.3	280.6	286.7
60°	183.8	189.1	192.9	198.9	205.0	214.8	223.9	235.3	246.6	253.4	261.0
62.5°	164.1	166.4	168.7	174.7	180.8	189.9	198.9	210.3	222.4	226.2	232.2
65°	144.5	146.7	150.5	155.8	160.4	165.7	175.5	184.6	195.9	202.0	204.2
67.5°	127.8	130.1	130.9	134.6	138.4	144.5	149.8	158.9	169.4	173.2	177.8
70°	108.9	112.7	113.5	116.5	118.0	121.8	127.8	134.6	143.0	149.8	153.6
72.5°	87.0	92.3	93.8	98.3	100.6	104.4	108.9	114.2	119.5	122.5	125.6
75°	71.1	72.6	73.4	77.2	80.9	86.2	88.5	91.5	96.1	99.8	102.9
77.5°	59.0	59.8	60.5	60.5	61.3	64.3	68.8	72.6	75.6	77.2	79.4
80°	47.7	46.9	46.9	47.7	47.7	47.7	49.2	54.5	56.0	59.8	59.0
82.5°	37.1	35.6	36.3	35.6	35.6	35.6	35.6	36.3	36.3	38.6	40.1
85°	24.2	25.0	24.2	24.2	23.4	24.2	23.4	23.4	22.7	22.7	21.9
87.5°	12.9	13.6	12.9	12.9	12.1	12.9	12.1	12.1	11.3	11.3	9.8
90°	26.5	25.5	24.5	23.5	24.5	21.6	18.6	15.7	12.7	11.8	10.8
92.5°	65.6	75.4	97.0	136.2	182.2	201.8	150.9	98.9	67.6	58.8	50.0
95°	187.1	239.0	352.7	471.2	580.9	517.3	356.6	210.6	127.4	108.2	89.1
97.5°	482.0	611.3	810.2	923.8	893.4	667.1	396.8	227.3	145.0	124.0	102.9
100°	961.0	1075.7	1155.0	1120.7	927.7	627.0	369.3	224.3	155.8	136.7	117.6
102.5°	1231.4	1286.3	1269.6	1130.5	864.1	568.2	345.8	228.3	168.5	151.4	134.2
105°	1390.1	1371.5	1273.6	1068.8	787.6	522.2	337.0	236.1	183.2	168.0	152.8
107.5°	1445.0	1368.6	1214.8	980.6	720.0	488.8	335.0	248.8	201.8	187.6	173.4
110°	1426.4	1302.9	1122.7	898.3	664.2	471.2	339.9	265.5	221.4	207.7	194.0

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1358.8	1216.7	1031.6	826.8	627.0	461.4	349.7	282.1	242.0	228.8	215.5
115°	1267.7	1123.7	953.2	772.0	602.5	460.4	360.5	300.8	263.5	250.3	237.1
117.5°	1175.6	1043.3	892.5	735.7	585.8	461.4	374.2	320.3	283.1	270.8	258.6
120°	1096.2	978.7	846.4	708.3	575.1	465.3	389.9	339.0	303.7	291.4	279.2
122.5°	1033.5	926.8	810.2	685.8	568.2	472.2	404.6	358.6	324.3	311.0	297.8
125°	979.7	885.6	778.8	667.1	562.3	479.1	420.3	377.2	342.9	329.6	316.4
127.5°	933.6	847.4	750.4	649.5	559.4	486.9	433.0	393.8	360.5	347.3	334.1
130°	891.5	812.1	724.0	635.8	556.4	494.7	445.7	408.5	376.2	363.0	349.7
132.5°	851.3	778.8	699.5	623.1	555.5	500.6	457.5	421.3	389.9	377.2	364.4
135°	811.2	747.5	677.9	612.3	554.5	506.5	467.3	434.0	403.6	390.4	377.2
137.5°	772.9	716.1	657.3	602.5	552.5	510.4	475.1	442.8	413.4	401.2	388.9
140°	736.7	689.7	639.7	593.7	551.5	514.3	481.0	451.6	423.2	411.0	398.7
142.5°	703.4	664.2	623.1	585.8	549.6	517.3	486.9	458.5	431.0	419.8	408.5
145°	674.0	642.7	610.3	579.0	547.6	518.2	490.8	464.4	438.9	427.6	416.4
147.5°	652.5	626.0	599.5	572.1	544.7	518.2	493.7	469.3	445.7	436.0	426.2
150°	630.9	610.3	587.8	565.3	540.8	518.2	494.7	474.2	451.6	442.8	434.0
152.5°	613.3	595.6	577.0	557.4	535.9	515.3	496.7	477.1	458.5	450.2	441.8
155°	596.6	581.9	566.2	549.6	530.0	513.3	496.7	481.0	464.4	457.5	450.6
157.5°	580.0	568.2	554.5	540.8	525.1	510.4	497.7	483.0	469.3	463.9	458.5
160°	565.3	555.5	544.7	532.0	519.2	508.4	497.7	485.9	474.2	469.3	464.4
162.5°	550.6	541.7	532.9	523.1	513.3	504.5	496.7	486.9	477.1	473.2	469.3
165°	535.9	529.0	523.1	515.3	507.5	500.6	494.7	487.9	480.0	476.6	473.2
167.5°	523.1	519.2	514.3	507.5	501.6	496.7	493.7	487.9	482.0	479.6	477.1
170°	512.4	508.4	505.5	500.6	495.7	492.8	490.8	486.9	482.0	481.0	480.0
172.5°	502.6	499.6	497.7	493.7	490.8	489.8	489.8	486.9	483.0	482.5	482.0
175°	493.7	491.8	490.8	488.8	486.9	486.9	487.9	485.9	483.9	483.4	483.0
177.5°	487.9	486.9	485.9	484.9	483.9	484.9	486.9	484.9	483.9	483.9	483.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	883.5	883.5	883.5	883.5
2.5°	860.8	866.1	876.7	885.8
5°	842.7	851.0	866.9	882.8
7.5°	820.7	833.6	854.0	876.0
10°	799.6	816.2	841.2	866.9
12.5°	778.4	795.8	822.2	855.5
15°	753.4	771.6	803.3	843.4
17.5°	731.5	755.7	784.4	824.5
20°	708.0	726.2	763.2	805.6
22.5°	678.5	708.8	743.6	788.2
25°	655.1	681.5	716.3	767.0
27.5°	626.3	657.3	699.7	744.3
30°	602.9	628.6	667.9	721.6
32.5°	575.6	605.9	646.8	699.7
35°	551.4	577.2	615.7	669.4
37.5°	522.7	550.7	593.8	641.5
40°	497.7	525.0	565.8	610.4
42.5°	467.5	496.2	537.1	574.9
45°	443.3	469.7	502.3	537.1
47.5°	413.8	441.8	473.5	497.7
50°	387.3	413.0	438.0	458.4
52.5°	358.5	382.0	404.7	419.8
55°	332.1	350.2	368.4	379.0
57.5°	301.1	318.5	333.6	339.6
60°	273.8	288.2	298.0	304.8
62.5°	245.1	255.7	263.2	267.0
65°	217.1	224.7	228.4	232.2
67.5°	188.4	195.2	197.4	202.0
70°	158.1	165.7	167.2	169.4
72.5°	135.4	135.4	138.4	141.5
75°	108.2	109.7	111.2	111.2
77.5°	84.7	84.7	86.2	87.0
80°	62.0	62.8	62.8	62.0
82.5°	42.4	43.9	42.4	41.6
85°	23.4	26.5	25.0	25.0
87.5°	9.8	9.8	11.3	9.8
90°	8.8	5.9	3.9	2.0
92.5°	40.2	31.3	21.6	14.7
95°	63.7	47.0	36.2	33.3
97.5°	77.4	62.7	53.9	52.9
100°	94.0	80.3	73.5	72.5
102.5°	113.6	100.9	95.0	93.1
105°	134.2	122.5	116.6	113.6
107.5°	155.8	144.0	138.1	135.2
110°	177.3	166.5	161.6	158.7



TEST NUMBER: P1012554

CATALOG NUMBER: S123RDIP-B560D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	198.9	188.1	183.2	180.3
115°	220.4	210.6	204.7	200.8
117.5°	240.0	231.2	226.3	221.4
120°	260.6	250.8	245.9	243.0
122.5°	280.2	269.4	264.5	261.6
125°	297.8	287.0	281.2	279.2
127.5°	313.5	302.7	295.9	292.9
130°	329.2	317.4	308.6	305.7
132.5°	343.9	329.2	319.4	315.4
135°	356.6	341.9	331.1	327.2
137.5°	368.4	352.7	341.9	338.0
140°	379.1	363.5	353.7	348.8
142.5°	388.9	375.2	364.4	360.5
145°	399.7	385.0	376.2	373.2
147.5°	409.5	396.8	387.9	386.0
150°	420.3	407.5	399.7	398.7
152.5°	430.1	419.3	411.5	411.5
155°	439.9	430.1	424.2	424.2
157.5°	448.7	439.9	435.0	434.0
160°	457.5	449.7	445.7	445.7
162.5°	463.4	457.5	454.6	454.6
165°	469.3	464.4	462.4	463.4
167.5°	474.2	470.2	469.3	470.2
170°	478.1	475.1	474.2	476.1
172.5°	481.0	479.1	479.1	480.0
175°	483.0	481.0	482.0	483.0
177.5°	483.9	483.0	483.9	484.9
180°	483.9	483.9	483.9	483.9

(END OF REPORT)