

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012570

Luminaire Tested: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012570
REPORT IS A COMBINATION OF REPORTS P993347 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1025UB40-4F0-XX-W2A-A
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6240.0 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	31	31	31
1	95	91	87	84	86	82	79	77	66	64	62	52	50	49	38	38	37	26	26	26
2	87	80	74	69	78	72	68	63	59	55	52	46	44	42	34	33	32	23	23	23
3	79	70	64	58	72	64	58	53	52	48	44	41	38	36	31	29	27	20	20	20
4	73	63	55	49	66	57	51	46	46	42	38	37	34	31	28	26	24	18	18	18
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	16	16	16
6	62	50	42	37	56	46	39	34	38	33	29	30	26	24	23	21	19	14	14	14
7	57	45	38	32	51	41	35	30	34	29	26	27	24	21	21	19	17	13	13	13
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15	11	11	11
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	15	14	10	10	10
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	12			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9536	9536	9536	9536
5°	9544	10983	9567	8148
10°	9459	13257	9500	7117
15°	9361	15047	9361	6275
20°	9170	16230	9221	5566
25°	9029	15420	9011	5079
30°	8866	10684	8847	4603
35°	8669	6859	8629	4244
40°	8424	4844	8383	3886
45°	7997	3876	7987	3538
50°	7474	3243	7449	3131
55°	6885	2673	6831	2654
60°	6308	2209	6244	2257
65°	5630	1767	5666	1914
70°	5003	1228	5139	1547
75°	4241	911	4413	1190
80°	3377	605	3665	891
85°	2401	286	2622	554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 12731 cd/sqm

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.4
10°-20°	272.3	4.4
20°-30°	428.9	6.9
30°-40°	446.0	7.1
40°-50°	381.6	6.1
50°-60°	290.9	4.7
60°-70°	186.4	3.0
70°-80°	89.3	1.4
80°-90°	26.1	0.4
90°-100°	46.6	0.7
100°-110°	225.5	3.6
110°-120°	552.5	8.9
120°-130°	701.4	11.2
130°-140°	749.3	12.0
140°-150°	700.6	11.2
150°-160°	565.1	9.1
160°-170°	364.7	5.8
170°-180°	125.7	2.0
0°-30°	788.3	12.6
0°-40°	1234.3	19.8
0°-60°	1906.8	30.6
0°-90°	2208.6	35.4
90°-120°	824.6	13.2
90°-150°	2975.8	47.7
90°-180°	4031.0	64.6
0°-180°	6240.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	886	886	886	886	886	
5°	885	1052	887	780	885	84
15°	846	1495	846	624	846	238
25°	769	1540	768	507	769	354
35°	671	668	668	413	671	420
45°	538	356	538	325	538	415
55°	380	224	377	222	380	341
65°	233	129	234	140	233	233
75°	112	55	116	71	112	120
85°	25	13	27	25	25	28
90°	1	30	1	30	1	5
95°	60	37	60	37	60	72
105°	293	43	293	43	293	310
115°	549	578	549	578	549	542
125°	774	790	774	790	774	692
135°	964	974	964	974	964	742
145°	1112	1123	1112	1123	1112	696
155°	1225	1223	1225	1223	1225	564
165°	1292	1289	1292	1289	1292	365
175°	1322	1318	1322	1318	1322	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9
2.5°	888.2	894.3	898.8	901.9	909.4	914.0	917.8	924.6	924.6	926.1	929.2
5°	885.2	898.1	907.2	919.3	935.2	942.8	953.4	962.5	975.4	982.3	989.1
7.5°	878.3	896.5	915.5	933.7	957.2	972.4	983.0	1006.5	1023.2	1043.7	1059.6
10°	869.2	894.3	918.5	946.6	978.5	1001.2	1017.1	1048.2	1080.1	1108.9	1133.2
12.5°	857.9	888.2	923.1	957.2	1002.0	1024.7	1050.5	1089.2	1134.7	1171.1	1203.7
15°	845.7	880.6	920.1	961.8	1017.9	1049.8	1086.9	1134.0	1184.8	1237.1	1281.9
17.5°	826.8	870.8	914.7	975.4	1041.4	1060.4	1092.2	1156.7	1219.7	1266.7	1321.3
20°	807.8	857.1	912.5	967.1	1038.4	1082.4	1112.0	1180.2	1247.7	1304.6	1357.0
22.5°	790.4	841.9	899.6	968.6	1035.3	1079.3	1116.5	1187.8	1265.9	1329.6	1394.1
25°	769.1	825.2	889.0	954.2	1035.3	1068.7	1109.7	1192.4	1275.0	1348.6	1428.2
27.5°	746.4	803.2	866.2	933.0	1007.3	1056.6	1096.8	1185.5	1286.4	1365.3	1447.2
30°	723.6	782.0	842.7	902.6	986.0	1033.1	1079.3	1177.2	1292.5	1382.7	1445.7
32.5°	701.6	750.9	810.8	869.2	951.9	1003.5	1055.8	1168.8	1294.8	1370.6	1400.9
35°	671.3	722.8	771.4	833.6	917.0	967.8	1029.3	1168.1	1284.9	1331.9	1316.8
37.5°	643.2	686.4	732.7	788.1	873.8	939.8	1003.5	1148.4	1252.3	1255.3	1169.6
40°	612.1	647.8	686.4	744.8	837.4	902.6	971.6	1118.0	1193.1	1148.4	997.4
42.5°	576.5	608.3	638.7	695.5	796.4	869.2	943.6	1080.1	1107.4	1004.2	847.2
45°	538.5	564.3	592.4	652.3	753.2	825.2	899.6	1021.7	993.6	848.0	698.6
47.5°	499.1	521.1	548.4	603.0	706.9	780.5	851.0	938.3	867.0	710.7	585.6
50°	459.6	477.1	503.6	559.8	659.9	726.6	791.9	848.8	748.6	609.8	483.9
52.5°	421.0	434.6	461.9	509.7	606.8	670.5	717.5	739.5	637.9	503.6	420.2
55°	380.0	395.2	413.4	461.9	558.3	605.3	636.4	635.6	530.9	427.0	347.4
57.5°	340.6	354.2	370.1	418.7	496.8	528.7	555.2	542.3	443.0	349.7	298.1
60°	305.7	313.3	330.7	371.7	430.8	458.1	473.3	451.3	361.8	295.1	246.5
62.5°	267.7	275.3	289.7	328.4	364.8	379.2	392.1	364.1	298.8	240.4	210.9
65°	232.9	242.7	251.8	282.9	302.6	320.1	318.6	295.1	233.6	195.7	171.4
67.5°	202.5	206.3	213.9	232.9	242.0	254.9	255.6	229.1	188.1	159.3	144.9
70°	169.9	173.7	179.0	188.1	194.2	197.2	195.7	172.2	141.8	124.4	111.5
72.5°	141.8	141.1	144.9	144.9	150.9	150.2	145.6	127.4	107.7	93.3	85.7
75°	111.5	112.3	113.0	111.5	109.2	106.2	102.4	88.7	75.8	69.0	62.2
77.5°	87.2	85.7	86.5	81.2	78.1	75.1	69.8	63.0	52.3	50.8	47.8
80°	62.2	61.4	60.7	58.4	51.6	48.5	44.8	41.0	38.7	37.2	36.4
82.5°	41.7	41.7	40.2	35.6	31.9	29.6	28.8	27.3	25.0	25.0	24.3
85°	25.0	24.3	22.8	18.2	15.9	15.9	15.9	15.9	14.4	14.4	13.7
87.5°	9.9	9.1	6.8	6.8	6.1	6.1	6.1	5.3	5.3	4.6	4.6
90°	1.0	3.2	5.4	7.5	9.7	10.8	12.2	15.1	17.9	20.8	23.6
92.5°	22.6	21.3	20.0	18.7	17.4	16.7	17.7	19.6	21.6	23.5	25.5
95°	59.9	50.9	42.0	33.0	24.1	19.6	20.8	23.2	25.7	28.1	30.5
97.5°	109.1	103.0	96.8	90.7	84.6	81.5	75.9	64.8	53.7	42.5	31.4
100°	166.0	170.4	174.8	179.1	183.5	185.7	168.7	134.6	100.5	66.5	32.4
102.5°	230.9	233.7	236.5	239.4	242.2	243.6	224.6	186.6	148.7	110.7	72.7
105°	292.8	295.2	297.6	300.0	302.4	303.6	293.8	274.1	254.5	234.8	215.2
107.5°	358.6	360.6	362.5	364.5	366.4	367.4	369.0	372.3	375.6	378.9	382.2
110°	424.4	426.2	427.9	429.7	431.4	432.3	433.5	435.9	438.3	440.7	443.1

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	487.3	488.8	490.4	491.9	493.4	494.2	495.4	497.8	500.2	502.6	505.0
115°	549.2	550.5	551.8	553.1	554.4	555.1	556.1	558.0	560.0	561.9	563.9
117.5°	610.1	611.6	613.2	614.7	616.2	617.0	617.5	618.6	619.7	620.8	621.9
120°	666.1	668.1	670.0	672.0	673.9	674.9	675.2	675.9	676.6	677.2	677.9
122.5°	723.1	724.6	726.2	727.7	729.2	730.0	730.4	731.3	732.2	733.0	733.9
125°	774.2	775.9	777.7	779.4	781.1	782.0	782.4	783.3	784.2	785.1	786.0
127.5°	825.3	827.0	828.8	830.5	832.2	833.1	833.6	834.7	835.8	836.9	838.0
130°	872.4	874.2	875.9	877.7	879.4	880.3	880.7	881.6	882.5	883.3	884.2
132.5°	917.6	919.4	921.1	922.9	924.6	925.5	925.8	926.5	927.1	927.8	928.4
135°	963.8	965.1	966.4	967.7	969.0	969.7	970.1	971.0	971.9	972.7	973.6
137.5°	1003.1	1004.8	1006.6	1008.3	1010.0	1010.9	1011.1	1011.6	1012.0	1012.5	1012.9
140°	1042.4	1043.7	1045.0	1046.3	1047.6	1048.3	1048.6	1049.3	1049.9	1050.6	1051.2
142.5°	1078.7	1080.0	1081.3	1082.6	1083.9	1084.6	1084.9	1085.6	1086.3	1086.9	1087.6
145°	1112.1	1113.6	1115.2	1116.7	1118.2	1119.0	1119.2	1119.7	1120.1	1120.6	1121.0
147.5°	1144.5	1145.6	1146.7	1147.8	1148.9	1149.5	1149.7	1150.1	1150.6	1151.0	1151.4
150°	1174.0	1174.7	1175.3	1176.0	1176.7	1177.0	1177.2	1177.6	1178.1	1178.5	1178.9
152.5°	1200.5	1200.7	1200.9	1201.2	1201.4	1201.5	1201.6	1201.8	1202.1	1202.3	1202.5
155°	1225.1	1224.7	1224.2	1223.8	1223.3	1223.1	1223.2	1223.4	1223.7	1223.9	1224.1
157.5°	1244.8	1244.8	1244.8	1244.8	1244.8	1244.8	1244.7	1244.5	1244.2	1244.0	1243.8
160°	1262.4	1262.2	1262.0	1261.8	1261.6	1261.5	1261.4	1261.2	1260.9	1260.7	1260.5
162.5°	1279.1	1278.5	1277.8	1277.2	1276.5	1276.2	1276.1	1275.9	1275.6	1275.4	1275.2
165°	1291.9	1291.3	1290.6	1290.0	1289.3	1289.0	1288.9	1288.7	1288.4	1288.2	1288.0
167.5°	1302.7	1301.8	1301.0	1300.1	1299.2	1298.8	1298.8	1298.8	1298.8	1298.8	1298.8
170°	1311.6	1310.7	1309.8	1308.9	1308.0	1307.6	1307.6	1307.6	1307.6	1307.6	1307.6
172.5°	1317.5	1316.4	1315.3	1314.2	1313.1	1312.5	1312.6	1312.8	1313.1	1313.3	1313.5
175°	1322.4	1321.3	1320.2	1319.1	1318.0	1317.5	1317.6	1317.8	1318.0	1318.2	1318.4
177.5°	1324.3	1323.2	1322.1	1321.0	1319.9	1319.4	1319.5	1319.7	1320.0	1320.2	1320.4
180°	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9
2.5°	935.2	935.2	942.1	948.9	945.1	947.4	955.7	952.7	958.7	958.0	960.3
5°	1005.8	1014.1	1020.9	1035.3	1037.6	1035.3	1049.8	1053.6	1060.4	1052.0	1055.8
7.5°	1085.4	1102.9	1119.5	1140.8	1147.6	1149.1	1156.7	1167.3	1176.4	1159.7	1168.1
10°	1162.8	1189.3	1223.5	1242.4	1259.1	1265.2	1271.2	1278.1	1288.7	1298.5	1291.0
12.5°	1246.2	1284.9	1317.5	1351.6	1372.1	1369.8	1387.3	1391.8	1400.2	1402.5	1405.5
15°	1314.5	1369.1	1389.6	1440.4	1444.9	1460.1	1479.8	1497.3	1499.5	1495.0	1495.0
17.5°	1379.7	1426.7	1463.1	1504.1	1512.4	1525.3	1550.4	1558.7	1561.7	1561.0	1561.0
20°	1432.8	1463.9	1525.3	1559.5	1573.1	1589.8	1607.3	1617.9	1620.1	1623.2	1618.6
22.5°	1467.7	1514.7	1564.8	1592.8	1604.2	1610.3	1621.7	1624.7	1620.9	1621.7	1622.4
25°	1495.0	1541.3	1571.6	1579.2	1578.4	1570.8	1562.5	1548.1	1546.6	1540.5	1528.4
27.5°	1502.6	1520.0	1516.2	1485.1	1454.0	1451.0	1400.9	1373.6	1342.5	1347.1	1329.6
30°	1461.6	1438.9	1385.0	1306.1	1273.5	1220.4	1164.3	1105.9	1083.1	1058.1	1104.4
32.5°	1361.5	1280.3	1184.8	1082.4	1027.8	980.7	920.8	878.3	854.1	833.6	873.0
35°	1210.6	1083.9	957.2	860.1	815.4	772.9	716.8	695.5	665.2	668.2	672.0
37.5°	1016.4	876.8	781.3	685.7	656.1	638.7	597.7	565.1	554.5	551.4	551.4
40°	834.3	719.8	634.9	559.8	537.0	522.6	490.0	474.8	463.4	460.4	464.2
42.5°	690.2	592.4	526.4	476.3	460.4	442.2	428.6	409.6	407.3	402.0	408.8
45°	579.5	494.5	445.2	408.8	395.2	388.4	373.2	361.8	357.3	356.5	361.8
47.5°	491.5	425.5	382.3	359.5	348.9	342.1	329.2	324.6	320.1	321.6	319.3
50°	412.6	363.3	335.3	314.8	307.9	301.1	292.8	288.2	286.0	286.0	285.2
52.5°	354.2	313.3	295.1	276.1	273.1	269.3	260.2	257.1	253.3	252.6	255.6
55°	303.4	275.3	257.1	245.8	242.7	235.1	231.3	227.5	225.3	223.8	224.5
57.5°	259.4	238.2	226.0	216.2	210.9	207.8	201.0	200.2	198.7	198.7	198.0
60°	223.0	207.8	193.4	187.3	183.6	179.8	179.0	174.5	172.2	173.7	172.9
62.5°	188.9	176.7	168.4	161.6	159.3	156.3	154.0	152.5	150.2	150.9	150.9
65°	157.8	147.9	141.8	135.8	135.0	132.0	131.2	129.7	129.7	128.9	130.5
67.5°	129.7	122.9	117.6	113.8	111.5	112.3	109.2	106.9	106.9	106.2	108.5
70°	103.2	99.4	94.1	89.5	86.5	86.5	82.7	81.9	81.9	81.9	81.2
72.5°	79.6	72.8	70.5	69.0	69.0	69.0	67.5	67.5	66.7	67.5	66.7
75°	59.2	58.4	56.9	56.1	56.1	55.4	54.6	54.6	54.6	54.6	54.6
77.5°	46.3	46.3	44.8	44.0	44.0	44.0	43.2	43.2	42.5	42.5	42.5
80°	34.1	34.1	32.6	32.6	32.6	31.9	31.9	31.9	32.6	31.9	31.9
82.5°	23.5	23.5	22.8	23.5	22.8	22.0	22.0	22.0	21.2	22.0	22.0
85°	13.7	13.7	12.9	12.1	12.9	12.9	12.1	12.9	12.1	12.9	12.1
87.5°	5.3	4.6	4.6	4.6	3.8	4.6	3.8	3.8	4.6	3.8	4.6
90°	24.5	25.3	26.2	27.1	27.5	27.7	28.2	28.6	29.1	29.5	29.1
92.5°	27.0	28.6	30.1	31.6	32.4	32.5	32.7	33.0	33.2	33.4	33.2
95°	32.0	33.5	35.0	36.5	37.3	37.3	37.3	37.3	37.3	37.3	37.3
97.5°	33.2	34.9	36.7	38.4	39.3	39.4	39.6	39.9	40.1	40.3	40.1
100°	34.2	35.9	37.7	39.4	40.3	40.4	40.6	40.9	41.1	41.3	41.1
102.5°	65.5	58.3	51.1	43.9	40.3	40.5	40.9	41.4	41.8	42.2	41.8
105°	176.6	137.9	99.3	60.6	41.3	41.5	41.9	42.4	42.8	43.2	42.8
107.5°	348.6	315.0	281.3	247.7	230.9	216.6	188.0	159.4	130.8	102.2	130.8
110°	435.9	428.7	421.5	414.3	410.7	395.1	363.9	332.6	301.4	270.2	301.4

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	507.0	508.9	510.9	512.8	513.8	513.6	513.2	512.7	512.3	511.9	512.3
115°	566.1	568.3	570.4	572.6	573.7	574.1	575.0	575.9	576.8	577.7	576.8
117.5°	623.6	625.4	627.1	628.8	629.7	629.8	630.0	630.3	630.5	630.7	630.5
120°	679.6	681.4	683.1	684.8	685.7	685.7	685.7	685.7	685.7	685.7	685.7
122.5°	735.0	736.1	737.2	738.3	738.8	738.9	739.1	739.4	739.6	739.8	739.6
125°	786.4	786.8	787.3	787.7	787.9	788.1	788.6	789.0	789.5	789.9	789.5
127.5°	838.7	839.3	840.0	840.7	841.0	840.8	840.3	839.9	839.4	839.0	839.4
130°	885.1	885.9	886.8	887.7	888.1	887.9	887.5	887.0	886.6	886.2	886.6
132.5°	929.3	930.1	931.0	931.9	932.3	932.0	931.3	930.7	930.0	929.4	930.0
135°	974.3	974.9	975.6	976.3	976.6	976.3	975.6	974.9	974.3	973.6	974.3
137.5°	1014.0	1015.1	1016.2	1017.3	1017.8	1017.6	1017.1	1016.7	1016.2	1015.8	1016.2
140°	1052.1	1052.9	1053.8	1054.7	1055.1	1054.9	1054.5	1054.0	1053.6	1053.2	1053.6
142.5°	1088.2	1088.9	1089.5	1090.2	1090.5	1090.2	1089.5	1088.9	1088.2	1087.6	1088.2
145°	1121.4	1121.8	1122.3	1122.7	1122.9	1122.9	1122.9	1122.9	1122.9	1122.9	1122.9
147.5°	1151.8	1152.3	1152.7	1153.2	1153.4	1152.9	1151.8	1150.7	1149.6	1148.5	1149.6
150°	1179.3	1179.8	1180.2	1180.7	1180.9	1180.6	1179.9	1179.3	1178.6	1178.0	1178.6
152.5°	1203.4	1204.2	1205.1	1206.0	1206.4	1205.9	1204.8	1203.7	1202.6	1201.5	1202.6
155°	1225.2	1226.3	1227.4	1228.5	1229.0	1228.3	1227.0	1225.7	1224.4	1223.1	1224.4
157.5°	1245.1	1246.4	1247.7	1249.0	1249.7	1248.8	1247.1	1245.3	1243.6	1241.8	1243.6
160°	1261.8	1263.1	1264.4	1265.7	1266.4	1265.6	1264.1	1262.6	1261.0	1259.5	1261.0
162.5°	1276.7	1278.3	1279.8	1281.3	1282.1	1281.4	1280.1	1278.8	1277.5	1276.2	1277.5
165°	1289.7	1291.5	1293.2	1294.9	1295.8	1295.0	1293.5	1292.0	1290.5	1289.0	1290.5
167.5°	1300.6	1302.3	1304.1	1305.8	1306.7	1305.8	1304.1	1302.3	1300.6	1298.8	1300.6
170°	1309.4	1311.1	1312.9	1314.6	1315.5	1314.6	1312.9	1311.1	1309.4	1307.6	1309.4
172.5°	1315.3	1317.0	1318.8	1320.5	1321.4	1320.4	1318.4	1316.5	1314.5	1312.5	1314.5
175°	1319.9	1321.5	1323.0	1324.5	1325.3	1324.4	1322.7	1321.0	1319.2	1317.5	1319.2
177.5°	1322.2	1323.9	1325.7	1327.4	1328.3	1327.2	1325.0	1322.8	1320.6	1318.4	1320.6
180°	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9
2.5°	956.5	951.9	948.9	946.6	944.3	951.2	942.1	932.2	925.4	920.8	919.3
5°	1056.6	1046.7	1038.4	1031.6	1033.1	1033.1	1017.1	999.7	984.5	976.2	967.1
7.5°	1172.6	1162.0	1145.3	1141.5	1138.5	1119.5	1103.6	1071.8	1052.8	1033.8	1017.1
10°	1287.9	1274.3	1258.3	1253.0	1245.5	1221.9	1197.7	1156.7	1133.2	1098.3	1076.3
12.5°	1395.6	1378.9	1363.0	1359.2	1347.8	1327.4	1285.7	1243.2	1203.0	1165.8	1127.1
15°	1485.9	1481.3	1457.1	1441.9	1416.9	1388.8	1379.7	1322.1	1271.2	1232.6	1162.8
17.5°	1561.7	1540.5	1517.8	1507.9	1498.0	1465.4	1432.8	1373.6	1319.0	1262.1	1217.4
20°	1622.4	1598.9	1583.0	1568.6	1564.0	1526.9	1475.3	1422.9	1363.0	1299.3	1240.9
22.5°	1625.5	1622.4	1611.8	1603.5	1594.4	1570.1	1529.1	1463.9	1400.2	1330.4	1253.8
25°	1562.5	1558.0	1588.3	1580.7	1586.8	1577.7	1555.7	1501.1	1426.7	1344.8	1267.4
27.5°	1372.9	1419.1	1466.9	1483.6	1495.0	1527.6	1538.2	1507.9	1448.0	1360.7	1274.3
30°	1115.0	1176.4	1253.8	1295.5	1327.4	1388.0	1466.9	1476.8	1448.7	1378.9	1272.8
32.5°	875.3	931.4	993.6	1042.9	1085.4	1209.8	1316.0	1392.6	1406.3	1369.8	1276.5
35°	705.4	729.7	788.8	835.9	893.5	999.7	1124.9	1248.5	1331.9	1336.5	1265.2
37.5°	581.8	594.7	646.2	672.8	706.9	800.2	917.0	1078.6	1208.3	1269.7	1233.3
40°	481.6	511.2	540.8	556.0	580.2	644.7	757.0	883.6	1044.4	1158.2	1184.0
42.5°	417.9	430.8	449.8	471.0	486.2	542.3	617.4	733.5	878.3	1036.9	1108.2
45°	368.6	373.2	392.9	406.6	422.5	461.9	515.0	612.1	739.5	895.8	1017.1
47.5°	327.7	336.8	347.4	355.7	366.4	396.7	442.2	512.7	625.0	764.6	895.0
50°	291.3	296.6	310.2	314.0	321.6	342.8	377.7	431.6	524.1	635.6	770.6
52.5°	257.1	267.0	272.3	277.6	284.4	301.9	324.6	368.6	438.4	543.1	657.6
55°	230.6	233.6	241.2	245.8	251.1	263.2	282.9	315.5	370.1	453.6	562.0
57.5°	204.8	204.8	212.4	216.2	221.5	230.6	248.0	273.1	312.5	374.7	474.1
60°	177.5	178.2	184.3	188.9	190.4	199.5	213.9	233.6	264.0	309.5	390.6
62.5°	153.2	157.0	160.0	161.6	166.9	172.2	184.3	198.0	219.2	259.4	317.1
65°	132.7	133.5	135.8	137.3	139.6	145.6	154.7	163.8	182.0	211.6	258.6
67.5°	109.2	112.3	115.3	115.3	117.6	120.6	129.7	137.3	150.9	168.4	200.2
70°	81.9	83.4	88.0	90.3	93.3	98.6	103.2	107.7	118.3	131.2	155.5
72.5°	68.3	68.3	69.8	70.5	70.5	74.3	81.2	85.7	91.0	100.1	116.8
75°	54.6	54.6	56.9	56.1	57.6	59.2	59.9	63.0	66.0	72.8	82.7
77.5°	43.2	44.0	44.0	44.8	44.8	45.5	46.3	47.8	49.3	53.1	57.6
80°	31.9	32.6	32.6	33.4	33.4	34.1	34.9	35.6	37.2	38.7	41.0
82.5°	22.0	22.8	22.8	23.5	22.8	23.5	24.3	24.3	25.0	26.5	27.3
85°	12.9	12.9	13.7	12.9	12.9	12.9	13.7	13.7	14.4	16.7	16.7
87.5°	3.8	4.6	3.8	4.6	4.6	4.6	4.6	5.3	5.3	6.1	6.8
90°	28.6	28.2	27.7	27.5	27.1	26.2	25.3	24.5	23.6	20.8	17.9
92.5°	33.0	32.7	32.5	32.4	31.6	30.1	28.6	27.0	25.5	23.5	21.6
95°	37.3	37.3	37.3	37.3	36.5	35.0	33.5	32.0	30.5	28.1	25.7
97.5°	39.9	39.6	39.4	39.3	38.4	36.7	34.9	33.2	31.4	42.5	53.7
100°	40.9	40.6	40.4	40.3	39.4	37.7	35.9	34.2	32.4	66.5	100.5
102.5°	41.4	40.9	40.5	40.3	43.9	51.1	58.3	65.5	72.7	110.7	148.7
105°	42.4	41.9	41.5	41.3	60.6	99.3	137.9	176.6	215.2	234.8	254.5
107.5°	159.4	188.0	216.6	230.9	247.7	281.3	315.0	348.6	382.2	378.9	375.6
110°	332.6	363.9	395.1	410.7	414.3	421.5	428.7	435.9	443.1	440.7	438.3

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	512.7	513.2	513.6	513.8	512.8	510.9	508.9	507.0	505.0	502.6	500.2
115°	575.9	575.0	574.1	573.7	572.6	570.4	568.3	566.1	563.9	561.9	560.0
117.5°	630.3	630.0	629.8	629.7	628.8	627.1	625.4	623.6	621.9	620.8	619.7
120°	685.7	685.7	685.7	685.7	684.8	683.1	681.4	679.6	677.9	677.2	676.6
122.5°	739.4	739.1	738.9	738.8	738.3	737.2	736.1	735.0	733.9	733.0	732.2
125°	789.0	788.6	788.1	787.9	787.7	787.3	786.8	786.4	786.0	785.1	784.2
127.5°	839.9	840.3	840.8	841.0	840.7	840.0	839.3	838.7	838.0	836.9	835.8
130°	887.0	887.5	887.9	888.1	887.7	886.8	885.9	885.1	884.2	883.3	882.5
132.5°	930.7	931.3	932.0	932.3	931.9	931.0	930.1	929.3	928.4	927.8	927.1
135°	974.9	975.6	976.3	976.6	976.3	975.6	974.9	974.3	973.6	972.7	971.9
137.5°	1016.7	1017.1	1017.6	1017.8	1017.3	1016.2	1015.1	1014.0	1012.9	1012.5	1012.0
140°	1054.0	1054.5	1054.9	1055.1	1054.7	1053.8	1052.9	1052.1	1051.2	1050.6	1049.9
142.5°	1088.9	1089.5	1090.2	1090.5	1090.2	1089.5	1088.9	1088.2	1087.6	1086.9	1086.3
145°	1122.9	1122.9	1122.9	1122.9	1122.7	1122.3	1121.8	1121.4	1121.0	1120.6	1120.1
147.5°	1150.7	1151.8	1152.9	1153.4	1153.2	1152.7	1152.3	1151.8	1151.4	1151.0	1150.6
150°	1179.3	1179.9	1180.6	1180.9	1180.7	1180.2	1179.8	1179.3	1178.9	1178.5	1178.1
152.5°	1203.7	1204.8	1205.9	1206.4	1206.0	1205.1	1204.2	1203.4	1202.5	1202.3	1202.1
155°	1225.7	1227.0	1228.3	1229.0	1228.5	1227.4	1226.3	1225.2	1224.1	1223.9	1223.7
157.5°	1245.3	1247.1	1248.8	1249.7	1249.0	1247.7	1246.4	1245.1	1243.8	1244.0	1244.2
160°	1262.6	1264.1	1265.6	1266.4	1265.7	1264.4	1263.1	1261.8	1260.5	1260.7	1260.9
162.5°	1278.8	1280.1	1281.4	1282.1	1281.3	1279.8	1278.3	1276.7	1275.2	1275.4	1275.6
165°	1292.0	1293.5	1295.0	1295.8	1294.9	1293.2	1291.5	1289.7	1288.0	1288.2	1288.4
167.5°	1302.3	1304.1	1305.8	1306.7	1305.8	1304.1	1302.3	1300.6	1298.8	1298.8	1298.8
170°	1311.1	1312.9	1314.6	1315.5	1314.6	1312.9	1311.1	1309.4	1307.6	1307.6	1307.6
172.5°	1316.5	1318.4	1320.4	1321.4	1320.5	1318.8	1317.0	1315.3	1313.5	1313.3	1313.1
175°	1321.0	1322.7	1324.4	1325.3	1324.5	1323.0	1321.5	1319.9	1318.4	1318.2	1318.0
177.5°	1322.8	1325.0	1327.2	1328.3	1327.4	1325.7	1323.9	1322.2	1320.4	1320.2	1320.0
180°	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9
2.5°	917.0	913.2	909.4	909.4	901.1	893.5	889.7	891.2	886.7	880.6	874.5
5°	957.2	942.1	939.0	930.7	919.3	903.4	895.0	887.4	878.3	866.2	854.8
7.5°	994.4	974.7	964.0	955.7	933.7	911.7	893.5	881.4	865.4	847.2	833.6
10°	1042.9	1006.5	995.1	976.2	945.1	914.0	892.8	873.0	851.0	829.8	811.6
12.5°	1081.6	1039.9	1018.7	999.7	959.5	920.1	884.4	860.1	833.6	810.1	786.6
15°	1125.6	1078.6	1041.4	1018.7	967.8	920.1	879.9	845.7	816.1	787.3	766.8
17.5°	1146.8	1087.7	1071.0	1038.4	964.8	917.0	867.7	831.3	795.7	762.3	738.0
20°	1180.2	1111.2	1069.5	1047.5	982.3	911.7	854.1	812.3	775.2	739.5	713.7
22.5°	1182.5	1107.4	1080.1	1038.4	958.0	895.8	841.9	791.1	747.9	714.5	688.0
25°	1177.2	1100.6	1062.7	1029.3	962.5	886.7	817.7	767.6	725.1	686.4	655.3
27.5°	1174.9	1080.9	1045.2	1011.8	936.7	860.1	803.2	746.4	697.8	663.7	631.8
30°	1171.9	1059.6	1016.4	977.7	908.7	839.7	771.4	722.1	675.8	632.6	600.7
32.5°	1152.2	1030.8	986.8	945.8	871.5	802.5	748.6	696.3	646.2	606.0	577.2
35°	1146.1	1004.2	946.6	902.6	829.8	768.4	711.5	668.2	621.2	581.0	546.9
37.5°	1128.6	976.9	914.7	858.6	782.8	724.4	682.6	639.4	593.9	550.7	523.4
40°	1098.3	945.1	874.5	816.9	738.8	679.6	640.9	609.1	564.3	525.6	492.3
42.5°	1053.6	912.5	836.6	775.9	689.5	634.1	602.2	571.9	534.0	493.8	466.5
45°	1002.0	869.2	798.7	731.2	643.2	589.4	556.0	537.8	502.9	468.8	436.9
47.5°	931.4	824.5	754.7	684.9	595.4	543.1	516.5	498.3	474.1	436.9	411.1
50°	842.7	766.8	700.9	638.7	548.4	498.3	471.8	458.1	437.7	411.1	386.1
52.5°	744.1	700.1	645.5	587.8	500.6	453.6	429.3	418.7	403.5	378.5	357.3
55°	644.7	625.8	588.6	531.7	450.5	411.9	390.6	377.0	365.6	347.4	329.2
57.5°	556.0	546.9	521.1	477.1	408.8	368.6	350.4	341.3	332.2	318.6	300.4
60°	464.2	474.1	447.5	425.5	363.3	328.4	312.5	302.6	298.1	286.0	274.6
62.5°	384.6	393.7	378.5	361.8	317.8	286.7	276.9	267.7	264.7	254.1	242.7
65°	312.5	323.9	312.5	303.4	276.9	251.1	238.9	234.4	231.3	224.5	215.4
67.5°	248.8	260.2	254.9	243.5	235.1	213.9	207.1	202.5	201.0	195.7	188.1
70°	187.3	203.3	204.8	198.0	190.4	180.5	176.0	174.5	170.7	166.1	161.6
72.5°	135.0	153.2	154.0	154.0	149.4	149.4	144.9	142.6	142.6	138.0	132.7
75°	99.4	111.5	113.0	114.5	116.8	119.1	116.0	116.0	115.3	110.7	108.5
77.5°	66.0	76.6	80.4	85.7	88.7	88.7	90.3	91.8	90.3	88.0	86.5
80°	42.5	50.1	54.6	57.6	62.2	64.5	66.7	67.5	66.0	65.2	63.0
82.5°	28.1	30.3	32.6	36.4	41.7	45.5	45.5	44.8	46.3	45.5	44.8
85°	15.9	17.4	18.2	19.0	22.0	25.8	26.5	27.3	28.8	27.3	25.8
87.5°	6.1	6.8	6.8	6.8	8.3	9.1	11.4	14.4	13.7	12.1	12.1
90°	15.1	12.2	10.8	9.7	7.5	5.4	3.2	1.0	3.2	5.4	7.5
92.5°	19.6	17.7	16.7	17.4	18.7	20.0	21.3	22.6	21.3	20.0	18.7
95°	23.2	20.8	19.6	24.1	33.0	42.0	50.9	59.9	50.9	42.0	33.0
97.5°	64.8	75.9	81.5	84.6	90.7	96.8	103.0	109.1	103.0	96.8	90.7
100°	134.6	168.7	185.7	183.5	179.1	174.8	170.4	166.0	170.4	174.8	179.1
102.5°	186.6	224.6	243.6	242.2	239.4	236.5	233.7	230.9	233.7	236.5	239.4
105°	274.1	293.8	303.6	302.4	300.0	297.6	295.2	292.8	295.2	297.6	300.0
107.5°	372.3	369.0	367.4	366.4	364.5	362.5	360.6	358.6	360.6	362.5	364.5
110°	435.9	433.5	432.3	431.4	429.7	427.9	426.2	424.4	426.2	427.9	429.7

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	497.8	495.4	494.2	493.4	491.9	490.4	488.8	487.3	488.8	490.4	491.9
115°	558.0	556.1	555.1	554.4	553.1	551.8	550.5	549.2	550.5	551.8	553.1
117.5°	618.6	617.5	617.0	616.2	614.7	613.2	611.6	610.1	611.6	613.2	614.7
120°	675.9	675.2	674.9	673.9	672.0	670.0	668.1	666.1	668.1	670.0	672.0
122.5°	731.3	730.4	730.0	729.2	727.7	726.2	724.6	723.1	724.6	726.2	727.7
125°	783.3	782.4	782.0	781.1	779.4	777.7	775.9	774.2	775.9	777.7	779.4
127.5°	834.7	833.6	833.1	832.2	830.5	828.8	827.0	825.3	827.0	828.8	830.5
130°	881.6	880.7	880.3	879.4	877.7	875.9	874.2	872.4	874.2	875.9	877.7
132.5°	926.5	925.8	925.5	924.6	922.9	921.1	919.4	917.6	919.4	921.1	922.9
135°	971.0	970.1	969.7	969.0	967.7	966.4	965.1	963.8	965.1	966.4	967.7
137.5°	1011.6	1011.1	1010.9	1010.0	1008.3	1006.6	1004.8	1003.1	1004.8	1006.6	1008.3
140°	1049.3	1048.6	1048.3	1047.6	1046.3	1045.0	1043.7	1042.4	1043.7	1045.0	1046.3
142.5°	1085.6	1084.9	1084.6	1083.9	1082.6	1081.3	1080.0	1078.7	1080.0	1081.3	1082.6
145°	1119.7	1119.2	1119.0	1118.2	1116.7	1115.2	1113.6	1112.1	1113.6	1115.2	1116.7
147.5°	1150.1	1149.7	1149.5	1148.9	1147.8	1146.7	1145.6	1144.5	1145.6	1146.7	1147.8
150°	1177.6	1177.2	1177.0	1176.7	1176.0	1175.3	1174.7	1174.0	1174.7	1175.3	1176.0
152.5°	1201.8	1201.6	1201.5	1201.4	1201.2	1200.9	1200.7	1200.5	1200.7	1200.9	1201.2
155°	1223.4	1223.2	1223.1	1223.3	1223.8	1224.2	1224.7	1225.1	1224.7	1224.2	1223.8
157.5°	1244.5	1244.7	1244.8	1244.8	1244.8	1244.8	1244.8	1244.8	1244.8	1244.8	1244.8
160°	1261.2	1261.4	1261.5	1261.6	1261.8	1262.0	1262.2	1262.4	1262.2	1262.0	1261.8
162.5°	1275.9	1276.1	1276.2	1276.5	1277.2	1277.8	1278.5	1279.1	1278.5	1277.8	1277.2
165°	1288.7	1288.9	1289.0	1289.3	1290.0	1290.6	1291.3	1291.9	1291.3	1290.6	1290.0
167.5°	1298.8	1298.8	1298.8	1299.2	1300.1	1301.0	1301.8	1302.7	1301.8	1301.0	1300.1
170°	1307.6	1307.6	1307.6	1308.0	1308.9	1309.8	1310.7	1311.6	1310.7	1309.8	1308.9
172.5°	1312.8	1312.6	1312.5	1313.1	1314.2	1315.3	1316.4	1317.5	1316.4	1315.3	1314.2
175°	1317.8	1317.6	1317.5	1318.0	1319.1	1320.2	1321.3	1322.4	1321.3	1320.2	1319.1
177.5°	1319.7	1319.5	1319.4	1319.9	1321.0	1322.1	1323.2	1324.3	1323.2	1322.1	1321.0
180°	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9
2.5°	874.5	870.8	869.2	865.4	856.3	850.3	843.4	838.9	839.7	835.9	838.1
5°	847.2	846.5	841.2	833.6	820.7	813.9	801.7	795.7	792.6	793.4	788.8
7.5°	824.5	817.7	813.9	801.7	789.6	775.2	765.3	760.0	755.5	750.9	747.9
10°	798.7	792.6	786.6	773.7	757.0	743.3	729.7	724.4	717.5	714.5	712.2
12.5°	771.4	767.6	760.0	744.8	725.9	713.0	697.1	694.0	684.9	678.9	677.3
15°	746.4	744.1	730.4	713.0	694.0	681.1	667.5	658.4	643.2	646.2	640.9
17.5°	719.8	710.0	701.6	678.1	669.0	649.3	633.3	628.8	618.2	611.3	604.5
20°	690.2	684.2	673.5	658.4	636.4	613.6	601.5	593.9	587.8	577.2	574.2
22.5°	662.2	654.6	645.5	625.8	606.8	587.8	571.1	564.3	556.7	549.2	544.6
25°	640.2	628.8	618.9	594.7	575.7	559.8	549.2	537.8	527.2	522.6	521.1
27.5°	606.0	599.2	589.4	566.6	549.2	531.7	521.8	514.3	502.9	497.6	493.0
30°	584.0	570.4	559.0	540.8	523.4	504.4	495.3	486.2	479.4	472.5	467.2
32.5°	554.5	543.8	534.7	516.5	499.1	481.6	471.8	458.1	454.3	449.0	443.0
35°	525.6	518.8	509.0	489.2	470.3	458.1	447.5	434.6	430.1	426.3	421.0
37.5°	498.3	488.5	481.6	462.7	446.0	431.6	423.2	412.6	409.6	405.0	401.2
40°	474.8	465.0	458.1	439.2	421.7	406.6	401.2	390.6	386.1	380.8	378.5
42.5°	448.3	439.9	430.8	417.2	399.0	383.8	373.2	367.1	361.0	358.8	354.2
45°	420.2	412.6	405.8	390.6	371.7	361.0	351.9	343.6	339.0	335.3	332.2
47.5°	395.9	389.1	380.0	363.3	348.1	338.3	329.2	320.8	316.3	311.7	307.9
50°	367.9	364.1	354.2	338.3	323.9	312.5	304.2	296.6	293.5	288.2	282.2
52.5°	342.8	336.0	327.7	314.8	301.9	288.2	276.9	272.3	267.0	264.0	258.6
55°	313.3	308.7	299.6	288.2	274.6	263.2	254.9	248.8	242.0	238.9	232.1
57.5°	288.2	279.9	275.3	260.9	248.0	236.7	230.6	224.5	216.9	212.4	209.3
60°	260.9	253.3	246.5	234.4	225.3	213.1	204.0	198.7	193.4	187.3	184.3
62.5°	234.4	228.3	220.0	210.1	198.7	188.9	182.0	174.5	171.4	165.4	163.1
65°	205.6	201.0	194.2	182.8	173.7	165.4	158.5	152.5	149.4	147.1	145.6
67.5°	179.8	173.7	169.1	159.3	149.4	142.6	138.8	135.0	131.2	128.9	126.7
70°	153.2	148.7	144.1	135.0	128.2	122.1	119.1	116.0	113.8	111.5	109.2
72.5°	125.9	123.6	119.1	113.0	107.7	103.2	100.9	97.1	94.8	91.0	89.5
75°	103.9	100.1	97.8	92.5	88.0	84.2	81.2	76.6	73.6	72.1	71.3
77.5°	81.9	80.4	77.4	72.8	70.5	66.7	62.2	60.7	59.2	59.2	58.4
80°	61.4	59.2	56.9	53.1	50.8	47.8	47.8	47.8	47.0	47.8	47.0
82.5°	41.7	40.2	38.7	36.4	35.6	35.6	36.4	36.4	36.4	36.4	36.4
85°	24.3	24.3	24.3	25.0	24.3	24.3	25.0	25.8	25.0	25.0	24.3
87.5°	11.4	11.4	12.1	12.1	12.9	12.9	12.9	12.9	12.9	12.9	13.7
90°	9.7	10.8	12.2	15.1	17.9	20.8	23.6	24.5	25.3	26.2	27.1
92.5°	17.4	16.7	17.7	19.6	21.6	23.5	25.5	27.0	28.6	30.1	31.6
95°	24.1	19.6	20.8	23.2	25.7	28.1	30.5	32.0	33.5	35.0	36.5
97.5°	84.6	81.5	75.9	64.8	53.7	42.5	31.4	33.2	34.9	36.7	38.4
100°	183.5	185.7	168.7	134.6	100.5	66.5	32.4	34.2	35.9	37.7	39.4
102.5°	242.2	243.6	224.6	186.6	148.7	110.7	72.7	65.5	58.3	51.1	43.9
105°	302.4	303.6	293.8	274.1	254.5	234.8	215.2	176.6	137.9	99.3	60.6
107.5°	366.4	367.4	369.0	372.3	375.6	378.9	382.2	348.6	315.0	281.3	247.7
110°	431.4	432.3	433.5	435.9	438.3	440.7	443.1	435.9	428.7	421.5	414.3

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	493.4	494.2	495.4	497.8	500.2	502.6	505.0	507.0	508.9	510.9	512.8
115°	554.4	555.1	556.1	558.0	560.0	561.9	563.9	566.1	568.3	570.4	572.6
117.5°	616.2	617.0	617.5	618.6	619.7	620.8	621.9	623.6	625.4	627.1	628.8
120°	673.9	674.9	675.2	675.9	676.6	677.2	677.9	679.6	681.4	683.1	684.8
122.5°	729.2	730.0	730.4	731.3	732.2	733.0	733.9	735.0	736.1	737.2	738.3
125°	781.1	782.0	782.4	783.3	784.2	785.1	786.0	786.4	786.8	787.3	787.7
127.5°	832.2	833.1	833.6	834.7	835.8	836.9	838.0	838.7	839.3	840.0	840.7
130°	879.4	880.3	880.7	881.6	882.5	883.3	884.2	885.1	885.9	886.8	887.7
132.5°	924.6	925.5	925.8	926.5	927.1	927.8	928.4	929.3	930.1	931.0	931.9
135°	969.0	969.7	970.1	971.0	971.9	972.7	973.6	974.3	974.9	975.6	976.3
137.5°	1010.0	1010.9	1011.1	1011.6	1012.0	1012.5	1012.9	1014.0	1015.1	1016.2	1017.3
140°	1047.6	1048.3	1048.6	1049.3	1049.9	1050.6	1051.2	1052.1	1052.9	1053.8	1054.7
142.5°	1083.9	1084.6	1084.9	1085.6	1086.3	1086.9	1087.6	1088.2	1088.9	1089.5	1090.2
145°	1118.2	1119.0	1119.2	1119.7	1120.1	1120.6	1121.0	1121.4	1121.8	1122.3	1122.7
147.5°	1148.9	1149.5	1149.7	1150.1	1150.6	1151.0	1151.4	1151.8	1152.3	1152.7	1153.2
150°	1176.7	1177.0	1177.2	1177.6	1178.1	1178.5	1178.9	1179.3	1179.8	1180.2	1180.7
152.5°	1201.4	1201.5	1201.6	1201.8	1202.1	1202.3	1202.5	1203.4	1204.2	1205.1	1206.0
155°	1223.3	1223.1	1223.2	1223.4	1223.7	1223.9	1224.1	1225.2	1226.3	1227.4	1228.5
157.5°	1244.8	1244.8	1244.7	1244.5	1244.2	1244.0	1243.8	1245.1	1246.4	1247.7	1249.0
160°	1261.6	1261.5	1261.4	1261.2	1260.9	1260.7	1260.5	1261.8	1263.1	1264.4	1265.7
162.5°	1276.5	1276.2	1276.1	1275.9	1275.6	1275.4	1275.2	1276.7	1278.3	1279.8	1281.3
165°	1289.3	1289.0	1288.9	1288.7	1288.4	1288.2	1288.0	1289.7	1291.5	1293.2	1294.9
167.5°	1299.2	1298.8	1298.8	1298.8	1298.8	1298.8	1298.8	1300.6	1302.3	1304.1	1305.8
170°	1308.0	1307.6	1307.6	1307.6	1307.6	1307.6	1307.6	1309.4	1311.1	1312.9	1314.6
172.5°	1313.1	1312.5	1312.6	1312.8	1313.1	1313.3	1313.5	1315.3	1317.0	1318.8	1320.5
175°	1318.0	1317.5	1317.6	1317.8	1318.0	1318.2	1318.4	1319.9	1321.5	1323.0	1324.5
177.5°	1319.9	1319.4	1319.5	1319.7	1320.0	1320.2	1320.4	1322.2	1323.9	1325.7	1327.4
180°	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9
2.5°	837.4	838.1	835.9	831.3	830.6	832.1	836.6	835.1	831.3	838.1	832.1
5°	791.1	787.3	785.8	787.3	782.8	780.5	785.0	782.8	785.0	785.8	788.1
7.5°	746.4	747.1	742.6	743.3	737.3	738.8	738.8	738.8	741.1	742.6	745.6
10°	707.7	709.2	703.9	704.6	700.1	697.1	699.3	703.9	703.9	703.9	705.4
12.5°	676.6	669.8	666.0	665.2	659.9	658.4	662.9	664.4	668.2	668.2	670.5
15°	637.9	636.4	633.3	633.3	620.5	623.5	625.0	630.3	637.9	631.8	633.3
17.5°	603.0	599.2	595.4	593.9	592.4	587.8	593.9	593.1	597.7	598.5	600.7
20°	571.9	568.9	561.3	562.0	563.6	556.7	560.5	560.5	565.1	569.6	574.9
22.5°	541.6	538.5	534.7	536.3	531.7	530.2	530.2	534.0	539.3	543.1	542.3
25°	518.1	512.7	510.5	508.2	505.9	507.4	505.2	509.0	512.7	515.0	512.7
27.5°	491.5	489.2	484.7	482.4	478.6	480.1	481.6	484.7	487.0	487.0	489.2
30°	465.7	462.7	461.2	458.9	458.9	455.9	456.6	459.6	461.9	464.2	467.2
32.5°	440.7	438.4	436.1	436.1	434.6	433.9	433.1	437.7	437.7	442.2	442.2
35°	420.2	416.4	416.4	412.6	414.1	413.4	411.9	414.9	415.7	418.7	417.9
37.5°	397.5	397.5	395.9	392.1	389.1	389.9	393.7	393.7	395.9	395.2	397.5
40°	374.7	373.2	373.2	370.9	370.1	369.4	370.1	370.9	374.7	373.9	374.7
42.5°	351.9	352.7	348.9	348.9	348.9	346.6	347.4	348.1	349.7	351.2	353.5
45°	329.9	328.4	327.7	326.2	324.6	325.4	324.6	327.7	326.9	328.4	330.7
47.5°	306.4	304.2	303.4	300.4	300.4	301.9	301.1	303.4	304.2	306.4	304.9
50°	283.7	280.6	278.4	279.1	274.6	276.1	276.1	278.4	280.6	281.4	282.9
52.5°	257.1	256.4	255.6	251.8	251.1	250.3	251.1	251.8	254.9	257.1	257.9
55°	231.3	230.6	226.0	224.5	222.2	222.2	223.8	224.5	229.8	230.6	233.6
57.5°	207.8	205.6	200.2	199.5	199.5	199.5	197.2	200.2	201.8	205.6	205.6
60°	182.0	182.0	177.5	177.5	178.2	177.5	177.5	178.2	178.2	181.3	182.8
62.5°	161.6	160.8	160.8	159.3	158.5	159.3	158.5	158.5	159.3	161.6	163.8
65°	143.4	142.6	141.8	141.1	139.6	139.6	140.3	141.8	141.8	143.4	144.1
67.5°	125.9	125.9	124.4	124.4	123.6	122.9	123.6	122.9	125.9	125.9	126.7
70°	108.5	107.7	105.4	104.7	102.4	103.2	103.2	105.4	106.2	107.7	109.2
72.5°	87.2	87.2	85.7	84.2	85.0	83.4	83.4	84.2	84.2	86.5	87.2
75°	72.1	70.5	69.8	70.5	69.8	71.3	69.8	69.8	71.3	71.3	71.3
77.5°	59.2	59.2	58.4	58.4	59.2	58.4	59.2	59.2	59.2	58.4	59.2
80°	48.5	47.8	47.8	47.8	47.0	47.0	47.0	47.0	47.0	47.0	47.0
82.5°	36.4	36.4	35.6	36.4	36.4	35.6	36.4	35.6	35.6	36.4	36.4
85°	24.3	25.8	24.3	24.3	25.0	25.0	25.8	25.0	25.8	24.3	25.0
87.5°	12.9	13.7	13.7	12.9	12.9	13.7	13.7	13.7	14.4	12.9	13.7
90°	27.5	27.7	28.2	28.6	29.1	29.5	29.1	28.6	28.2	27.7	27.5
92.5°	32.4	32.5	32.7	33.0	33.2	33.4	33.2	33.0	32.7	32.5	32.4
95°	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3	37.3
97.5°	39.3	39.4	39.6	39.9	40.1	40.3	40.1	39.9	39.6	39.4	39.3
100°	40.3	40.4	40.6	40.9	41.1	41.3	41.1	40.9	40.6	40.4	40.3
102.5°	40.3	40.5	40.9	41.4	41.8	42.2	41.8	41.4	40.9	40.5	40.3
105°	41.3	41.5	41.9	42.4	42.8	43.2	42.8	42.4	41.9	41.5	41.3
107.5°	230.9	216.6	188.0	159.4	130.8	102.2	130.8	159.4	188.0	216.6	230.9
110°	410.7	395.1	363.9	332.6	301.4	270.2	301.4	332.6	363.9	395.1	410.7

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	513.8	513.6	513.2	512.7	512.3	511.9	512.3	512.7	513.2	513.6	513.8
115°	573.7	574.1	575.0	575.9	576.8	577.7	576.8	575.9	575.0	574.1	573.7
117.5°	629.7	629.8	630.0	630.3	630.5	630.7	630.5	630.3	630.0	629.8	629.7
120°	685.7	685.7	685.7	685.7	685.7	685.7	685.7	685.7	685.7	685.7	685.7
122.5°	738.8	738.9	739.1	739.4	739.6	739.8	739.6	739.4	739.1	738.9	738.8
125°	787.9	788.1	788.6	789.0	789.5	789.9	789.5	789.0	788.6	788.1	787.9
127.5°	841.0	840.8	840.3	839.9	839.4	839.0	839.4	839.9	840.3	840.8	841.0
130°	888.1	887.9	887.5	887.0	886.6	886.2	886.6	887.0	887.5	887.9	888.1
132.5°	932.3	932.0	931.3	930.7	930.0	929.4	930.0	930.7	931.3	932.0	932.3
135°	976.6	976.3	975.6	974.9	974.3	973.6	974.3	974.9	975.6	976.3	976.6
137.5°	1017.8	1017.6	1017.1	1016.7	1016.2	1015.8	1016.2	1016.7	1017.1	1017.6	1017.8
140°	1055.1	1054.9	1054.5	1054.0	1053.6	1053.2	1053.6	1054.0	1054.5	1054.9	1055.1
142.5°	1090.5	1090.2	1089.5	1088.9	1088.2	1087.6	1088.2	1088.9	1089.5	1090.2	1090.5
145°	1122.9	1122.9	1122.9	1122.9	1122.9	1122.9	1122.9	1122.9	1122.9	1122.9	1122.9
147.5°	1153.4	1152.9	1151.8	1150.7	1149.6	1148.5	1149.6	1150.7	1151.8	1152.9	1153.4
150°	1180.9	1180.6	1179.9	1179.3	1178.6	1178.0	1178.6	1179.3	1179.9	1180.6	1180.9
152.5°	1206.4	1205.9	1204.8	1203.7	1202.6	1201.5	1202.6	1203.7	1204.8	1205.9	1206.4
155°	1229.0	1228.3	1227.0	1225.7	1224.4	1223.1	1224.4	1225.7	1227.0	1228.3	1229.0
157.5°	1249.7	1248.8	1247.1	1245.3	1243.6	1241.8	1243.6	1245.3	1247.1	1248.8	1249.7
160°	1266.4	1265.6	1264.1	1262.6	1261.0	1259.5	1261.0	1262.6	1264.1	1265.6	1266.4
162.5°	1282.1	1281.4	1280.1	1278.8	1277.5	1276.2	1277.5	1278.8	1280.1	1281.4	1282.1
165°	1295.8	1295.0	1293.5	1292.0	1290.5	1289.0	1290.5	1292.0	1293.5	1295.0	1295.8
167.5°	1306.7	1305.8	1304.1	1302.3	1300.6	1298.8	1300.6	1302.3	1304.1	1305.8	1306.7
170°	1315.5	1314.6	1312.9	1311.1	1309.4	1307.6	1309.4	1311.1	1312.9	1314.6	1315.5
172.5°	1321.4	1320.4	1318.4	1316.5	1314.5	1312.5	1314.5	1316.5	1318.4	1320.4	1321.4
175°	1325.3	1324.4	1322.7	1321.0	1319.2	1317.5	1319.2	1321.0	1322.7	1324.4	1325.3
177.5°	1328.3	1327.2	1325.0	1322.8	1320.6	1318.4	1320.6	1322.8	1325.0	1327.2	1328.3
180°	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9
2.5°	838.1	841.2	838.1	832.1	838.1	841.9	845.7	851.8	854.8	854.8	859.4
5°	790.4	796.4	794.1	792.6	798.7	802.5	808.6	816.1	824.5	829.8	835.9
7.5°	747.9	751.7	755.5	755.5	761.5	769.9	779.0	788.1	798.7	806.3	810.8
10°	710.7	713.7	716.0	719.1	728.2	737.3	749.4	760.8	769.9	778.2	785.8
12.5°	675.1	679.6	684.9	687.2	694.0	705.4	716.8	730.4	744.8	753.2	760.8
15°	640.9	643.2	649.3	656.1	662.2	674.3	688.7	703.1	715.3	728.2	735.0
17.5°	606.0	606.8	622.7	618.9	638.7	650.0	657.6	671.3	691.0	701.6	712.2
20°	571.9	579.5	586.3	590.1	600.7	613.6	635.6	646.2	662.2	672.0	681.1
22.5°	545.4	556.7	556.7	565.8	571.1	583.3	599.2	619.7	637.1	644.0	656.9
25°	521.8	527.2	536.3	539.3	549.2	559.8	570.4	592.4	611.3	620.5	629.6
27.5°	491.5	498.3	510.5	510.5	523.4	534.7	547.6	562.0	581.0	593.9	603.8
30°	468.0	474.8	480.1	488.5	493.8	504.4	527.2	537.8	554.5	565.8	578.0
32.5°	446.0	451.3	455.9	465.0	471.0	483.2	495.3	514.3	528.7	539.3	552.2
35°	421.7	427.0	433.1	439.9	449.0	460.4	471.8	487.7	502.1	512.0	522.6
37.5°	399.0	402.8	411.9	416.4	424.0	434.6	449.0	465.7	478.6	486.2	496.8
40°	377.0	380.0	386.8	395.2	400.5	408.8	424.0	438.4	454.3	463.4	471.8
42.5°	353.5	357.3	363.3	371.7	380.0	389.1	397.5	414.1	428.6	436.1	445.2
45°	333.0	335.3	339.8	348.1	356.5	363.3	376.2	391.4	405.0	411.1	421.0
47.5°	308.7	311.0	317.8	321.6	330.7	339.8	352.7	367.9	380.0	386.1	395.2
50°	283.7	286.0	290.5	298.8	304.9	314.8	326.2	339.0	354.2	362.6	367.9
52.5°	259.4	264.0	267.7	274.6	282.2	292.0	302.6	314.8	327.7	336.0	342.1
55°	235.1	238.9	243.5	247.3	256.4	265.5	277.6	289.0	300.4	307.9	314.8
57.5°	207.8	213.1	217.7	225.3	232.1	239.7	253.3	262.4	276.1	281.4	287.5
60°	184.3	189.6	193.4	199.5	205.6	215.4	224.5	235.9	247.3	254.1	261.7
62.5°	164.6	166.9	169.1	175.2	181.3	190.4	199.5	210.9	223.0	226.8	232.9
65°	144.9	147.1	150.9	156.3	160.8	166.1	176.0	185.1	196.5	202.5	204.8
67.5°	128.2	130.5	131.2	135.0	138.8	144.9	150.2	159.3	169.9	173.7	178.2
70°	109.2	113.0	113.8	116.8	118.3	122.1	128.2	135.0	143.4	150.2	154.0
72.5°	87.2	92.5	94.1	98.6	100.9	104.7	109.2	114.5	119.8	122.9	125.9
75°	71.3	72.8	73.6	77.4	81.2	86.5	88.7	91.8	96.3	100.1	103.2
77.5°	59.2	59.9	60.7	60.7	61.4	64.5	69.0	72.8	75.8	77.4	79.6
80°	47.8	47.0	47.0	47.8	47.8	47.8	49.3	54.6	56.1	59.9	59.2
82.5°	37.2	35.6	36.4	35.6	35.6	35.6	35.6	36.4	36.4	38.7	40.2
85°	24.3	25.0	24.3	24.3	23.5	24.3	23.5	23.5	22.8	22.8	22.0
87.5°	12.9	13.7	12.9	12.9	12.1	12.9	12.1	12.1	11.4	11.4	9.9
90°	27.1	26.2	25.3	24.5	23.6	20.8	17.9	15.1	12.2	10.8	9.7
92.5°	31.6	30.1	28.6	27.0	25.5	23.5	21.6	19.6	17.7	16.7	17.4
95°	36.5	35.0	33.5	32.0	30.5	28.1	25.7	23.2	20.8	19.6	24.1
97.5°	38.4	36.7	34.9	33.2	31.4	42.5	53.7	64.8	75.9	81.5	84.6
100°	39.4	37.7	35.9	34.2	32.4	66.5	100.5	134.6	168.7	185.7	183.5
102.5°	43.9	51.1	58.3	65.5	72.7	110.7	148.7	186.6	224.6	243.6	242.2
105°	60.6	99.3	137.9	176.6	215.2	234.8	254.5	274.1	293.8	303.6	302.4
107.5°	247.7	281.3	315.0	348.6	382.2	378.9	375.6	372.3	369.0	367.4	366.4
110°	414.3	421.5	428.7	435.9	443.1	440.7	438.3	435.9	433.5	432.3	431.4

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	512.8	510.9	508.9	507.0	505.0	502.6	500.2	497.8	495.4	494.2	493.4
115°	572.6	570.4	568.3	566.1	563.9	561.9	560.0	558.0	556.1	555.1	554.4
117.5°	628.8	627.1	625.4	623.6	621.9	620.8	619.7	618.6	617.5	617.0	616.2
120°	684.8	683.1	681.4	679.6	677.9	677.2	676.6	675.9	675.2	674.9	673.9
122.5°	738.3	737.2	736.1	735.0	733.9	733.0	732.2	731.3	730.4	730.0	729.2
125°	787.7	787.3	786.8	786.4	786.0	785.1	784.2	783.3	782.4	782.0	781.1
127.5°	840.7	840.0	839.3	838.7	838.0	836.9	835.8	834.7	833.6	833.1	832.2
130°	887.7	886.8	885.9	885.1	884.2	883.3	882.5	881.6	880.7	880.3	879.4
132.5°	931.9	931.0	930.1	929.3	928.4	927.8	927.1	926.5	925.8	925.5	924.6
135°	976.3	975.6	974.9	974.3	973.6	972.7	971.9	971.0	970.1	969.7	969.0
137.5°	1017.3	1016.2	1015.1	1014.0	1012.9	1012.5	1012.0	1011.6	1011.1	1010.9	1010.0
140°	1054.7	1053.8	1052.9	1052.1	1051.2	1050.6	1049.9	1049.3	1048.6	1048.3	1047.6
142.5°	1090.2	1089.5	1088.9	1088.2	1087.6	1086.9	1086.3	1085.6	1084.9	1084.6	1083.9
145°	1122.7	1122.3	1121.8	1121.4	1121.0	1120.6	1120.1	1119.7	1119.2	1119.0	1118.2
147.5°	1153.2	1152.7	1152.3	1151.8	1151.4	1151.0	1150.6	1150.1	1149.7	1149.5	1148.9
150°	1180.7	1180.2	1179.8	1179.3	1178.9	1178.5	1178.1	1177.6	1177.2	1177.0	1176.7
152.5°	1206.0	1205.1	1204.2	1203.4	1202.5	1202.3	1202.1	1201.8	1201.6	1201.5	1201.4
155°	1228.5	1227.4	1226.3	1225.2	1224.1	1223.9	1223.7	1223.4	1223.2	1223.1	1223.3
157.5°	1249.0	1247.7	1246.4	1245.1	1243.8	1244.0	1244.2	1244.5	1244.7	1244.8	1244.8
160°	1265.7	1264.4	1263.1	1261.8	1260.5	1260.7	1260.9	1261.2	1261.4	1261.5	1261.6
162.5°	1281.3	1279.8	1278.3	1276.7	1275.2	1275.4	1275.6	1275.9	1276.1	1276.2	1276.5
165°	1294.9	1293.2	1291.5	1289.7	1288.0	1288.2	1288.4	1288.7	1288.9	1289.0	1289.3
167.5°	1305.8	1304.1	1302.3	1300.6	1298.8	1298.8	1298.8	1298.8	1298.8	1298.8	1299.2
170°	1314.6	1312.9	1311.1	1309.4	1307.6	1307.6	1307.6	1307.6	1307.6	1307.6	1308.0
172.5°	1320.5	1318.8	1317.0	1315.3	1313.5	1313.3	1313.1	1312.8	1312.6	1312.5	1313.1
175°	1324.5	1323.0	1321.5	1319.9	1318.4	1318.2	1318.0	1317.8	1317.6	1317.5	1318.0
177.5°	1327.4	1325.7	1323.9	1322.2	1320.4	1320.2	1320.0	1319.7	1319.5	1319.4	1319.9
180°	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4	1322.4

TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	885.9	885.9	885.9	885.9
2.5°	863.2	868.5	879.1	888.2
5°	845.0	853.3	869.2	885.2
7.5°	823.0	835.9	856.3	878.3
10°	801.7	818.4	843.4	869.2
12.5°	780.5	797.9	824.5	857.9
15°	755.5	773.7	805.5	845.7
17.5°	733.5	757.7	786.6	826.8
20°	710.0	728.2	765.3	807.8
22.5°	680.4	710.7	745.6	790.4
25°	656.9	683.4	718.3	769.1
27.5°	628.0	659.1	701.6	746.4
30°	604.5	630.3	669.8	723.6
32.5°	577.2	607.6	648.5	701.6
35°	552.9	578.7	617.4	671.3
37.5°	524.1	552.2	595.4	643.2
40°	499.1	526.4	567.4	612.1
42.5°	468.8	497.6	538.5	576.5
45°	444.5	471.0	503.6	538.5
47.5°	414.9	443.0	474.8	499.1
50°	388.4	414.1	439.2	459.6
52.5°	359.5	383.0	405.8	421.0
55°	333.0	351.2	369.4	380.0
57.5°	301.9	319.3	334.5	340.6
60°	274.6	289.0	298.8	305.7
62.5°	245.8	256.4	264.0	267.7
65°	217.7	225.3	229.1	232.9
67.5°	188.9	195.7	198.0	202.5
70°	158.5	166.1	167.6	169.9
72.5°	135.8	135.8	138.8	141.8
75°	108.5	110.0	111.5	111.5
77.5°	85.0	85.0	86.5	87.2
80°	62.2	63.0	63.0	62.2
82.5°	42.5	44.0	42.5	41.7
85°	23.5	26.5	25.0	25.0
87.5°	9.9	9.9	11.4	9.9
90°	7.5	5.4	3.2	1.0
92.5°	18.7	20.0	21.3	22.6
95°	33.0	42.0	50.9	59.9
97.5°	90.7	96.8	103.0	109.1
100°	179.1	174.8	170.4	166.0
102.5°	239.4	236.5	233.7	230.9
105°	300.0	297.6	295.2	292.8
107.5°	364.5	362.5	360.6	358.6
110°	429.7	427.9	426.2	424.4



TEST NUMBER: P1012570

CATALOG NUMBER: S123RDIP-B560D1025UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	491.9	490.4	488.8	487.3
115°	553.1	551.8	550.5	549.2
117.5°	614.7	613.2	611.6	610.1
120°	672.0	670.0	668.1	666.1
122.5°	727.7	726.2	724.6	723.1
125°	779.4	777.7	775.9	774.2
127.5°	830.5	828.8	827.0	825.3
130°	877.7	875.9	874.2	872.4
132.5°	922.9	921.1	919.4	917.6
135°	967.7	966.4	965.1	963.8
137.5°	1008.3	1006.6	1004.8	1003.1
140°	1046.3	1045.0	1043.7	1042.4
142.5°	1082.6	1081.3	1080.0	1078.7
145°	1116.7	1115.2	1113.6	1112.1
147.5°	1147.8	1146.7	1145.6	1144.5
150°	1176.0	1175.3	1174.7	1174.0
152.5°	1201.2	1200.9	1200.7	1200.5
155°	1223.8	1224.2	1224.7	1225.1
157.5°	1244.8	1244.8	1244.8	1244.8
160°	1261.8	1262.0	1262.2	1262.4
162.5°	1277.2	1277.8	1278.5	1279.1
165°	1290.0	1290.6	1291.3	1291.9
167.5°	1300.1	1301.0	1301.8	1302.7
170°	1308.9	1309.8	1310.7	1311.6
172.5°	1314.2	1315.3	1316.4	1317.5
175°	1319.1	1320.2	1321.3	1322.4
177.5°	1321.0	1322.1	1323.2	1324.3
180°	1322.4	1322.4	1322.4	1322.4

(END OF REPORT)