

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012642

Luminaire Tested: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012642
REPORT IS A COMBINATION OF REPORTS P993440 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D585UB27-4F0-XX-W2A-A1
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4200.0 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	53	51	50
2	91	84	78	73	84	78	73	68	67	63	60	56	54	51	47	45	43
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38
4	76	66	58	52	70	61	55	50	53	48	44	45	41	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	40	60	50	43	38	43	38	34	37	33	30	32	28	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	23	21
9	52	40	33	28	48	38	31	27	33	28	24	29	25	21	25	21	19
10	49	37	30	25	45	35	28	24	31	25	22	27	22	20	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9510	9510	9510	9510
5°	9518	10953	9542	8126
10°	9434	13222	9475	7098
15°	9336	15006	9336	6258
20°	9145	16186	9196	5551
25°	9004	15378	8987	5066
30°	8841	10655	8823	4590
35°	8645	6841	8606	4232
40°	8401	4831	8359	3876
45°	7977	3865	7965	3528
50°	7454	3234	7430	3122
55°	6867	2665	6811	2647
60°	6289	2203	6227	2251
65°	5613	1763	5649	1908
70°	4989	1225	5124	1543
75°	4230	909	4401	1186
80°	3366	603	3654	889
85°	2401	286	2613	554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 12696 cd/sqm

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	2.1
10°-20°	271.6	6.5
20°-30°	427.8	10.2
30°-40°	444.8	10.6
40°-50°	380.6	9.1
50°-60°	290.1	6.9
60°-70°	185.9	4.4
70°-80°	89.1	2.1
80°-90°	24.9	0.6
90°-100°	46.4	1.1
100°-110°	140.5	3.3
110°-120°	239.2	5.7
120°-130°	314.7	7.5
130°-140°	353.8	8.4
140°-150°	347.8	8.3
150°-160°	292.8	7.0
160°-170°	194.9	4.6
170°-180°	68.3	1.6
0°-30°	786.1	18.7
0°-40°	1231.0	29.3
0°-60°	1901.6	45.3
0°-90°	2201.5	52.4
90°-120°	426.2	10.1
90°-150°	1442.5	34.3
90°-180°	1998.0	47.6
0°-180°	4200.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	884	884	884	884	884	
5°	883	1049	885	778	883	84
15°	843	1491	843	622	843	237
25°	767	1536	766	506	767	353
35°	669	666	666	412	669	419
45°	537	356	536	324	537	414
55°	379	223	376	222	379	340
65°	232	129	234	139	232	232
75°	111	54	116	71	111	120
85°	25	13	27	25	25	28
90°	1	17	1	17	1	4
95°	33	44	33	44	33	37
105°	128	135	128	135	128	136
115°	241	241	241	241	241	238
125°	352	348	352	348	352	314
135°	457	457	457	457	457	352
145°	555	555	555	555	555	346
155°	635	634	635	634	635	292
165°	692	690	692	690	692	195
175°	720	717	720	717	720	68
180°	721	721	721	721	721	

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	885.8	891.8	896.4	899.4	907.0	911.5	915.3	922.1	922.1	923.6	926.6
5°	882.8	895.6	904.7	916.8	932.7	940.2	950.8	959.9	972.8	979.6	986.4
7.5°	876.0	894.1	913.0	931.2	954.6	969.7	980.3	1003.8	1020.4	1040.9	1056.7
10°	866.9	891.8	916.0	944.0	975.8	998.5	1014.4	1045.4	1077.2	1105.9	1130.1
12.5°	855.5	885.8	920.6	954.6	999.2	1021.9	1047.7	1086.2	1131.6	1167.9	1200.5
15°	843.4	878.2	917.6	959.2	1015.1	1046.9	1084.0	1130.9	1181.5	1233.7	1278.4
17.5°	824.5	868.4	912.3	972.8	1038.6	1057.5	1089.3	1153.6	1216.3	1263.2	1317.7
20°	805.6	854.8	910.0	964.5	1035.6	1079.4	1108.9	1177.0	1244.3	1301.1	1353.3
22.5°	788.2	839.6	897.1	966.0	1032.5	1076.4	1113.5	1184.6	1262.5	1326.0	1390.3
25°	767.0	823.0	886.5	951.6	1032.5	1065.8	1106.7	1189.1	1271.6	1344.9	1424.4
27.5°	744.3	801.1	863.8	930.4	1004.5	1053.7	1093.8	1182.3	1282.9	1361.6	1443.3
30°	721.6	779.9	840.4	900.2	983.4	1030.3	1076.4	1174.0	1289.0	1379.0	1441.8
32.5°	699.7	748.9	808.6	866.9	949.3	1000.8	1053.0	1165.7	1291.2	1366.9	1397.1
35°	669.4	720.9	769.3	831.3	914.5	965.2	1026.5	1164.9	1281.4	1328.3	1313.2
37.5°	641.5	684.6	730.7	785.9	871.4	937.2	1000.8	1145.2	1248.9	1251.9	1166.4
40°	610.4	646.0	684.6	742.8	835.1	900.2	969.0	1115.0	1189.9	1145.2	994.7
42.5°	574.9	606.7	636.9	693.6	794.3	866.9	941.0	1077.2	1104.4	1001.5	844.9
45°	537.1	562.8	590.8	650.5	751.1	823.0	897.1	1018.9	990.9	845.7	696.7
47.5°	497.7	519.7	546.9	601.4	705.0	778.4	848.7	935.7	864.6	708.8	584.0
50°	458.4	475.8	502.3	558.2	658.1	724.7	789.7	846.4	746.6	608.2	482.6
52.5°	419.8	433.4	460.7	508.3	605.1	668.7	715.6	737.5	636.2	502.3	419.1
55°	379.0	394.1	412.3	460.7	556.7	603.6	634.6	633.9	529.5	425.9	346.4
57.5°	339.6	353.3	369.1	417.6	495.5	527.2	553.7	540.9	441.8	348.7	297.3
60°	304.8	312.4	329.8	370.7	429.7	456.9	472.0	450.1	360.8	294.3	245.8
62.5°	267.0	274.6	289.0	327.5	363.8	378.2	391.1	363.1	298.0	239.8	210.3
65°	232.2	242.1	251.1	282.1	301.8	319.2	317.7	294.3	233.0	195.2	171.0
67.5°	202.0	205.7	213.3	232.2	241.3	254.2	254.9	228.4	187.6	158.9	144.5
70°	169.4	173.2	178.5	187.6	193.6	196.7	195.2	171.7	141.5	124.1	111.2
72.5°	141.5	140.7	144.5	144.5	150.5	149.8	145.2	127.1	107.4	93.0	85.5
75°	111.2	112.0	112.7	111.2	108.9	105.9	102.1	88.5	75.6	68.8	62.0
77.5°	87.0	85.5	86.2	80.9	77.9	74.9	69.6	62.8	52.2	50.7	47.7
80°	62.0	61.3	60.5	58.2	51.4	48.4	44.6	40.8	38.6	37.1	36.3
82.5°	41.6	41.6	40.1	35.6	31.8	29.5	28.7	27.2	25.0	25.0	24.2
85°	25.0	24.2	22.7	18.2	15.9	15.9	15.9	15.9	14.4	14.4	13.6
87.5°	9.8	9.1	6.8	6.8	6.1	6.1	6.1	5.3	5.3	4.5	4.5
90°	0.6	1.8	3.1	4.3	5.6	6.2	7.0	8.7	10.3	12.0	13.6
92.5°	17.0	17.8	18.5	19.3	20.0	20.4	20.8	21.5	22.3	23.0	23.8
95°	33.4	34.3	35.2	36.1	37.0	37.4	37.9	38.9	39.9	40.9	41.9
97.5°	55.0	55.6	56.2	56.9	57.5	57.8	58.2	58.9	59.7	60.4	61.2
100°	77.1	77.9	78.6	79.4	80.1	80.5	80.8	81.4	82.1	82.7	83.3
102.5°	102.6	103.0	103.4	103.7	104.1	104.3	104.7	105.6	106.5	107.3	108.2
105°	127.5	127.7	128.0	128.2	128.5	128.6	129.2	130.3	131.4	132.6	133.7
107.5°	156.9	157.0	157.2	157.3	157.4	157.5	157.8	158.3	158.8	159.3	159.8
110°	184.1	184.4	184.6	184.9	185.2	185.3	185.4	185.7	185.9	186.2	186.4



TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	212.5	212.6	212.7	212.8	212.9	213.0	213.0	213.0	213.0	213.0	213.0
115°	240.8	241.2	241.6	241.9	242.3	242.5	242.4	242.1	241.9	241.6	241.4
117.5°	269.7	269.8	270.0	270.1	270.2	270.3	270.2	269.9	269.6	269.4	269.1
120°	296.3	297.1	297.8	298.6	299.3	299.7	299.4	298.8	298.1	297.5	296.9
122.5°	324.1	324.6	325.1	325.6	326.1	326.4	326.3	326.0	325.7	325.5	325.2
125°	352.4	352.8	353.2	353.5	353.9	354.1	354.0	353.7	353.5	353.2	353.0
127.5°	378.5	379.3	380.0	380.8	381.5	381.9	381.8	381.5	381.2	381.0	380.7
130°	404.5	405.5	406.5	407.6	408.6	409.1	408.9	408.5	408.2	407.8	407.4
132.5°	430.6	431.6	432.6	433.6	434.6	435.1	435.0	434.7	434.5	434.2	434.0
135°	457.2	458.0	458.7	459.5	460.2	460.6	460.5	460.4	460.3	460.2	460.1
137.5°	481.6	482.2	482.8	483.5	484.1	484.4	484.6	485.0	485.3	485.7	486.1
140°	507.1	507.7	508.3	509.0	509.6	509.9	510.0	510.1	510.2	510.4	510.5
142.5°	530.3	530.9	531.6	532.2	532.9	533.2	533.3	533.6	533.8	534.1	534.3
145°	554.7	554.9	555.2	555.4	555.7	555.8	556.0	556.4	556.7	557.1	557.5
147.5°	575.6	576.1	576.6	577.1	577.6	577.9	578.1	578.5	578.8	579.2	579.6
150°	597.7	598.0	598.2	598.5	598.8	598.9	599.0	599.3	599.5	599.8	600.0
152.5°	615.9	616.3	616.7	617.0	617.4	617.6	617.7	617.8	617.9	618.0	618.1
155°	635.1	635.1	635.1	635.1	635.1	635.1	635.2	635.3	635.4	635.6	635.7
157.5°	651.6	651.5	651.3	651.2	651.1	651.0	651.1	651.2	651.3	651.5	651.6
160°	666.9	666.6	666.4	666.1	665.8	665.7	665.7	665.7	665.7	665.7	665.7
162.5°	680.5	680.1	679.7	679.4	679.0	678.8	678.9	679.0	679.1	679.2	679.3
165°	691.8	691.4	691.0	690.7	690.3	690.1	690.1	690.1	690.1	690.1	690.1
167.5°	701.4	700.9	700.4	699.9	699.4	699.2	699.3	699.4	699.5	699.6	699.7
170°	709.4	708.9	708.4	707.9	707.4	707.1	707.1	707.1	707.1	707.1	707.1
172.5°	715.6	715.1	714.6	714.1	713.6	713.3	713.3	713.3	713.3	713.3	713.3
175°	719.6	719.1	718.6	718.1	717.6	717.3	717.3	717.3	717.3	717.3	717.3
177.5°	721.8	721.3	720.8	720.3	719.8	719.6	719.6	719.6	719.6	719.6	719.6
180°	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	932.7	932.7	939.5	946.3	942.5	944.8	953.1	950.1	956.1	955.4	957.6
5°	1003.0	1011.4	1018.2	1032.5	1034.8	1032.5	1046.9	1050.7	1057.5	1049.2	1053.0
7.5°	1082.5	1099.9	1116.5	1137.7	1144.5	1146.0	1153.6	1164.2	1173.2	1156.6	1164.9
10°	1159.6	1186.1	1220.1	1239.0	1255.7	1261.7	1267.8	1274.6	1285.2	1295.0	1287.5
12.5°	1242.8	1281.4	1313.9	1348.0	1368.4	1366.1	1383.5	1388.1	1396.4	1398.6	1401.7
15°	1310.9	1365.4	1385.8	1436.5	1441.0	1456.1	1475.8	1493.2	1495.5	1490.9	1490.9
17.5°	1376.0	1422.9	1459.2	1500.0	1508.3	1521.2	1546.2	1554.5	1557.5	1556.7	1556.7
20°	1428.9	1459.9	1521.2	1555.2	1568.8	1585.5	1602.9	1613.5	1615.7	1618.8	1614.2
22.5°	1463.7	1510.6	1560.5	1588.5	1599.9	1605.9	1617.3	1620.3	1616.5	1617.3	1618.0
25°	1490.9	1537.1	1567.3	1574.9	1574.1	1566.6	1558.3	1543.9	1542.4	1536.3	1524.2
27.5°	1498.5	1515.9	1512.1	1481.1	1450.1	1447.1	1397.1	1369.9	1338.9	1343.4	1326.0
30°	1457.6	1435.0	1381.2	1302.6	1270.1	1217.1	1161.1	1102.9	1080.2	1055.2	1101.4
32.5°	1357.8	1276.9	1181.5	1079.4	1025.0	978.1	918.3	876.0	851.7	831.3	870.7
35°	1207.3	1080.9	954.6	857.8	813.2	770.8	714.8	693.6	663.4	666.4	670.2
37.5°	1013.6	874.4	779.1	683.8	654.3	636.9	596.1	563.5	553.0	549.9	549.9
40°	832.1	717.9	633.1	558.2	535.6	521.2	488.7	473.5	462.2	459.2	462.9
42.5°	688.4	590.8	525.0	475.0	459.2	441.0	427.4	408.5	406.2	400.9	407.7
45°	577.9	493.2	444.0	407.7	394.1	387.3	372.2	360.8	356.3	355.5	360.8
47.5°	490.2	424.4	381.2	358.5	348.0	341.2	328.3	323.8	319.2	320.7	318.5
50°	411.5	362.3	334.3	313.9	307.1	300.3	292.0	287.4	285.2	285.2	284.4
52.5°	353.3	312.4	294.3	275.3	272.3	268.5	259.5	256.4	252.6	251.9	254.9
55°	302.6	274.6	256.4	245.1	242.1	234.5	230.7	226.9	224.7	223.1	223.9
57.5°	258.7	237.5	225.4	215.6	210.3	207.3	200.5	199.7	198.2	198.2	197.4
60°	222.4	207.3	192.9	186.8	183.1	179.3	178.5	174.0	171.7	173.2	172.5
62.5°	188.4	176.2	167.9	161.1	158.9	155.8	153.6	152.0	149.8	150.5	150.5
65°	157.3	147.5	141.5	135.4	134.6	131.6	130.9	129.4	129.4	128.6	130.1
67.5°	129.4	122.5	117.2	113.5	111.2	112.0	108.9	106.7	106.7	105.9	108.2
70°	102.9	99.1	93.8	89.3	86.2	86.2	82.5	81.7	81.7	81.7	80.9
72.5°	79.4	72.6	70.3	68.8	68.8	68.8	67.3	67.3	66.6	67.3	66.6
75°	59.0	58.2	56.7	56.0	56.0	55.2	54.5	54.5	54.5	54.5	54.5
77.5°	46.1	46.1	44.6	43.9	43.9	43.9	43.1	43.1	42.4	42.4	42.4
80°	34.0	34.0	32.5	32.5	32.5	31.8	31.8	31.8	32.5	31.8	31.8
82.5°	23.4	23.4	22.7	23.4	22.7	21.9	21.9	21.9	21.2	21.9	21.9
85°	13.6	13.6	12.9	12.1	12.9	12.9	12.1	12.9	12.1	12.9	12.1
87.5°	5.3	4.5	4.5	4.5	3.8	4.5	3.8	3.8	4.5	3.8	4.5
90°	14.1	14.6	15.1	15.6	15.9	16.0	16.3	16.5	16.8	17.0	16.8
92.5°	24.2	24.6	24.9	25.3	25.5	25.4	25.1	24.9	24.6	24.4	24.6
95°	42.4	42.9	43.4	43.9	44.2	44.2	44.2	44.2	44.2	44.2	44.2
97.5°	61.8	62.4	63.1	63.7	64.0	63.9	63.8	63.7	63.6	63.5	63.6
100°	83.7	84.1	84.4	84.8	85.0	85.1	85.4	85.6	85.9	86.1	85.9
102.5°	108.6	109.0	109.3	109.7	109.9	109.8	109.7	109.6	109.5	109.4	109.5
105°	133.7	133.7	133.7	133.7	133.7	133.8	134.1	134.3	134.6	134.8	134.6
107.5°	160.2	160.6	160.9	161.3	161.5	161.4	161.3	161.2	161.0	160.9	161.0
110°	186.9	187.4	187.9	188.4	188.7	188.6	188.3	188.0	187.8	187.5	187.8

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	213.6	214.3	214.9	215.6	215.9	215.9	215.9	215.9	215.9	215.9	215.9
115°	241.5	241.6	241.7	241.8	241.9	241.8	241.7	241.6	241.5	241.4	241.5
117.5°	269.1	269.1	269.1	269.1	269.1	268.9	268.5	268.2	267.8	267.4	267.8
120°	296.8	296.6	296.5	296.4	296.3	296.2	295.9	295.7	295.4	295.2	295.4
122.5°	324.8	324.4	324.1	323.7	323.5	323.3	322.9	322.6	322.2	321.8	322.2
125°	352.5	352.0	351.5	351.0	350.7	350.4	349.9	349.4	348.9	348.4	348.9
127.5°	379.9	379.2	378.4	377.7	377.3	377.1	376.6	376.1	375.6	375.1	375.6
130°	406.9	406.4	405.9	405.4	405.1	404.7	403.8	402.9	402.0	401.1	402.0
132.5°	433.4	432.8	432.1	431.5	431.2	430.9	430.2	429.6	428.9	428.3	428.9
135°	459.6	459.1	458.6	458.1	457.8	457.7	457.4	457.2	456.9	456.7	456.9
137.5°	485.5	484.9	484.2	483.6	483.3	483.1	482.7	482.4	482.0	481.6	482.0
140°	510.4	510.2	510.1	510.0	509.9	509.5	508.6	507.7	506.9	506.0	506.9
142.5°	534.2	534.0	533.9	533.8	533.7	533.4	532.8	532.1	531.5	530.9	531.5
145°	557.4	557.2	557.1	557.0	556.9	556.7	556.2	555.7	555.2	554.7	555.2
147.5°	579.6	579.6	579.6	579.6	579.6	579.2	578.5	577.7	577.0	576.2	577.0
150°	600.0	600.0	600.0	600.0	600.0	599.6	598.9	598.1	597.4	596.6	597.4
152.5°	618.4	618.6	618.9	619.2	619.3	619.0	618.3	617.7	617.0	616.4	617.0
155°	636.2	636.7	637.2	637.7	638.0	637.6	636.7	635.8	634.9	634.0	634.9
157.5°	652.1	652.6	653.1	653.6	653.8	653.4	652.7	651.9	651.2	650.4	651.2
160°	666.3	667.0	667.6	668.3	668.6	668.3	667.8	667.3	666.8	666.3	666.8
162.5°	679.9	680.6	681.2	681.9	682.2	681.8	680.9	680.0	679.1	678.2	679.1
165°	690.9	691.6	692.4	693.1	693.5	693.1	692.2	691.3	690.4	689.5	690.4
167.5°	700.5	701.2	702.0	702.7	703.1	702.7	702.0	701.2	700.5	699.7	700.5
170°	708.0	708.9	709.8	710.7	711.1	710.7	709.8	708.9	708.0	707.1	708.0
172.5°	714.1	714.8	715.6	716.3	716.7	716.3	715.4	714.5	713.7	712.8	713.7
175°	718.1	718.8	719.6	720.3	720.7	720.3	719.4	718.5	717.6	716.7	717.6
177.5°	720.4	721.1	721.9	722.6	723.0	722.6	721.7	720.8	719.9	719.0	719.9
180°	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	953.9	949.3	946.3	944.0	941.8	948.6	939.5	929.7	922.8	918.3	916.8
5°	1053.7	1043.9	1035.6	1028.7	1030.3	1030.3	1014.4	997.0	981.9	973.5	964.5
7.5°	1169.4	1158.9	1142.2	1138.4	1135.4	1116.5	1100.6	1068.8	1049.9	1031.0	1014.4
10°	1284.4	1270.8	1254.9	1249.6	1242.1	1218.6	1194.4	1153.6	1130.1	1095.3	1073.4
12.5°	1391.8	1375.2	1359.3	1355.5	1344.2	1323.8	1282.2	1239.8	1199.7	1162.6	1124.1
15°	1481.9	1477.3	1453.1	1438.0	1413.0	1385.0	1376.0	1318.5	1267.8	1229.2	1159.6
17.5°	1557.5	1536.3	1513.6	1503.8	1494.0	1461.4	1428.9	1369.9	1315.4	1258.7	1214.1
20°	1618.0	1594.6	1578.7	1564.3	1559.8	1522.7	1471.3	1419.1	1359.3	1295.8	1237.5
22.5°	1621.0	1618.0	1607.4	1599.1	1590.0	1565.8	1525.0	1459.9	1396.4	1326.8	1250.4
25°	1558.3	1553.7	1584.0	1576.4	1582.5	1573.4	1551.4	1497.0	1422.9	1341.2	1264.0
27.5°	1369.1	1415.3	1462.9	1479.6	1490.9	1523.5	1534.0	1503.8	1444.0	1357.0	1270.8
30°	1112.0	1173.2	1250.4	1292.0	1323.8	1384.3	1462.9	1472.8	1444.8	1375.2	1269.3
32.5°	872.9	928.9	990.9	1040.1	1082.5	1206.5	1312.4	1388.8	1402.4	1366.1	1273.1
35°	703.5	727.7	786.7	833.6	891.1	997.0	1121.8	1245.1	1328.3	1332.8	1261.7
37.5°	580.2	593.0	644.5	671.0	705.0	798.0	914.5	1075.6	1205.0	1266.3	1230.0
40°	480.3	509.8	539.3	554.5	578.7	643.0	754.9	881.2	1041.6	1155.1	1180.8
42.5°	416.8	429.7	448.6	469.7	484.9	540.9	615.7	731.5	876.0	1034.0	1105.1
45°	367.6	372.2	391.8	405.4	421.3	460.7	513.6	610.4	737.5	893.3	1014.4
47.5°	326.8	335.9	346.4	354.8	365.4	395.6	441.0	511.3	623.3	762.5	892.6
50°	290.5	295.8	309.4	313.2	320.7	341.9	376.7	430.4	522.7	633.9	768.5
52.5°	256.4	266.3	271.6	276.9	283.7	301.1	323.8	367.6	437.2	541.6	655.8
55°	230.0	233.0	240.5	245.1	250.4	262.5	282.1	314.7	369.1	452.3	560.5
57.5°	204.2	204.2	211.8	215.6	220.9	230.0	247.4	272.3	311.7	373.7	472.8
60°	177.0	177.8	183.8	188.4	189.9	198.9	213.3	233.0	263.2	308.6	389.6
62.5°	152.8	156.6	159.6	161.1	166.4	171.7	183.8	197.4	218.6	258.7	316.2
65°	132.4	133.1	135.4	136.9	139.2	145.2	154.3	163.4	181.5	211.0	257.9
67.5°	108.9	112.0	115.0	115.0	117.2	120.3	129.4	136.9	150.5	167.9	199.7
70°	81.7	83.2	87.7	90.0	93.0	98.3	102.9	107.4	118.0	130.9	155.1
72.5°	68.1	68.1	69.6	70.3	70.3	74.1	80.9	85.5	90.8	99.8	116.5
75°	54.5	54.5	56.7	56.0	57.5	59.0	59.8	62.8	65.8	72.6	82.5
77.5°	43.1	43.9	43.9	44.6	44.6	45.4	46.1	47.7	49.2	53.0	57.5
80°	31.8	32.5	32.5	33.3	33.3	34.0	34.8	35.6	37.1	38.6	40.8
82.5°	21.9	22.7	22.7	23.4	22.7	23.4	24.2	24.2	25.0	26.5	27.2
85°	12.9	12.9	13.6	12.9	12.9	12.9	13.6	13.6	14.4	16.6	16.6
87.5°	3.8	4.5	3.8	4.5	4.5	4.5	4.5	5.3	5.3	6.1	6.8
90°	16.5	16.3	16.0	15.9	15.6	15.1	14.6	14.1	13.6	12.0	10.3
92.5°	24.9	25.1	25.4	25.5	25.3	24.9	24.6	24.2	23.8	23.0	22.3
95°	44.2	44.2	44.2	44.2	43.9	43.4	42.9	42.4	41.9	40.9	39.9
97.5°	63.7	63.8	63.9	64.0	63.7	63.1	62.4	61.8	61.2	60.4	59.7
100°	85.6	85.4	85.1	85.0	84.8	84.4	84.1	83.7	83.3	82.7	82.1
102.5°	109.6	109.7	109.8	109.9	109.7	109.3	109.0	108.6	108.2	107.3	106.5
105°	134.3	134.1	133.8	133.7	133.7	133.7	133.7	133.7	133.7	132.6	131.4
107.5°	161.2	161.3	161.4	161.5	161.3	160.9	160.6	160.2	159.8	159.3	158.8
110°	188.0	188.3	188.6	188.7	188.4	187.9	187.4	186.9	186.4	186.2	185.9

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	215.9	215.9	215.9	215.9	215.6	214.9	214.3	213.6	213.0	213.0	213.0
115°	241.6	241.7	241.8	241.9	241.8	241.7	241.6	241.5	241.4	241.6	241.9
117.5°	268.2	268.5	268.9	269.1	269.1	269.1	269.1	269.1	269.1	269.4	269.6
120°	295.7	295.9	296.2	296.3	296.4	296.5	296.6	296.8	296.9	297.5	298.1
122.5°	322.6	322.9	323.3	323.5	323.7	324.1	324.4	324.8	325.2	325.5	325.7
125°	349.4	349.9	350.4	350.7	351.0	351.5	352.0	352.5	353.0	353.2	353.5
127.5°	376.1	376.6	377.1	377.3	377.7	378.4	379.2	379.9	380.7	381.0	381.2
130°	402.9	403.8	404.7	405.1	405.4	405.9	406.4	406.9	407.4	407.8	408.2
132.5°	429.6	430.2	430.9	431.2	431.5	432.1	432.8	433.4	434.0	434.2	434.5
135°	457.2	457.4	457.7	457.8	458.1	458.6	459.1	459.6	460.1	460.2	460.3
137.5°	482.4	482.7	483.1	483.3	483.6	484.2	484.9	485.5	486.1	485.7	485.3
140°	507.7	508.6	509.5	509.9	510.0	510.1	510.2	510.4	510.5	510.4	510.2
142.5°	532.1	532.8	533.4	533.7	533.8	533.9	534.0	534.2	534.3	534.1	533.8
145°	555.7	556.2	556.7	556.9	557.0	557.1	557.2	557.4	557.5	557.1	556.7
147.5°	577.7	578.5	579.2	579.6	579.6	579.6	579.6	579.6	579.6	579.2	578.8
150°	598.1	598.9	599.6	600.0	600.0	600.0	600.0	600.0	600.0	599.8	599.5
152.5°	617.7	618.3	619.0	619.3	619.2	618.9	618.6	618.4	618.1	618.0	617.9
155°	635.8	636.7	637.6	638.0	637.7	637.2	636.7	636.2	635.7	635.6	635.4
157.5°	651.9	652.7	653.4	653.8	653.6	653.1	652.6	652.1	651.6	651.5	651.3
160°	667.3	667.8	668.3	668.6	668.3	667.6	667.0	666.3	665.7	665.7	665.7
162.5°	680.0	680.9	681.8	682.2	681.9	681.2	680.6	679.9	679.3	679.2	679.1
165°	691.3	692.2	693.1	693.5	693.1	692.4	691.6	690.9	690.1	690.1	690.1
167.5°	701.2	702.0	702.7	703.1	702.7	702.0	701.2	700.5	699.7	699.6	699.5
170°	708.9	709.8	710.7	711.1	710.7	709.8	708.9	708.0	707.1	707.1	707.1
172.5°	714.5	715.4	716.3	716.7	716.3	715.6	714.8	714.1	713.3	713.3	713.3
175°	718.5	719.4	720.3	720.7	720.3	719.6	718.8	718.1	717.3	717.3	717.3
177.5°	720.8	721.7	722.6	723.0	722.6	721.9	721.1	720.4	719.6	719.6	719.6
180°	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	914.5	910.7	907.0	907.0	898.6	891.1	887.3	888.8	884.3	878.2	872.2
5°	954.6	939.5	936.5	928.1	916.8	900.9	892.6	885.0	876.0	863.8	852.5
7.5°	991.7	972.0	961.4	953.1	931.2	909.2	891.1	879.0	863.1	844.9	831.3
10°	1040.1	1003.8	992.4	973.5	942.5	911.5	890.3	870.7	848.7	827.5	809.4
12.5°	1078.7	1037.1	1015.9	997.0	956.9	917.6	882.0	857.8	831.3	807.9	784.4
15°	1122.5	1075.6	1038.6	1015.9	965.2	917.6	877.5	843.4	813.9	785.2	764.8
17.5°	1143.7	1084.7	1068.1	1035.6	962.2	914.5	865.4	829.1	793.5	760.2	736.0
20°	1177.0	1108.2	1066.6	1044.6	979.6	909.2	851.7	810.1	773.1	737.5	711.8
22.5°	1179.3	1104.4	1077.2	1035.6	955.4	893.3	839.6	789.0	745.8	712.6	686.1
25°	1174.0	1097.6	1059.8	1026.5	959.9	884.3	815.4	765.5	723.2	684.6	653.6
27.5°	1171.7	1077.9	1042.4	1009.1	934.2	857.8	801.1	744.3	695.9	661.9	630.1
30°	1168.7	1056.7	1013.6	975.0	906.2	837.4	769.3	720.1	674.0	630.9	599.1
32.5°	1149.0	1028.0	984.1	943.3	869.1	800.3	746.6	694.4	644.5	604.4	575.6
35°	1143.0	1001.5	944.0	900.2	827.5	766.3	709.5	666.4	619.5	579.4	545.4
37.5°	1125.6	974.3	912.3	856.3	780.6	722.4	680.8	637.7	592.3	549.2	521.9
40°	1095.3	942.5	872.2	814.7	736.8	677.8	639.2	607.4	562.8	524.2	490.9
42.5°	1050.7	910.0	834.3	773.8	687.6	632.4	600.6	570.4	532.5	492.4	465.2
45°	999.2	866.9	796.5	729.2	641.5	587.7	554.5	536.3	501.5	467.5	435.7
47.5°	928.9	822.2	752.7	683.1	593.8	541.6	515.1	497.0	472.8	435.7	410.0
50°	840.4	764.8	698.9	636.9	546.9	497.0	470.5	456.9	436.5	410.0	385.0
52.5°	742.1	698.2	643.7	586.2	499.2	452.3	428.1	417.6	402.4	377.5	356.3
55°	643.0	624.1	587.0	530.3	449.3	410.7	389.6	375.9	364.6	346.4	328.3
57.5°	554.5	545.4	519.7	475.8	407.7	367.6	349.5	340.4	331.3	317.7	299.5
60°	462.9	472.8	446.3	424.4	362.3	327.5	311.7	301.8	297.3	285.2	273.8
62.5°	383.5	392.6	377.5	360.8	316.9	285.9	276.1	267.0	264.0	253.4	242.1
65°	311.7	323.0	311.7	302.6	276.1	250.4	238.3	233.7	230.7	223.9	214.8
67.5°	248.1	259.5	254.2	242.8	234.5	213.3	206.5	202.0	200.5	195.2	187.6
70°	186.8	202.7	204.2	197.4	189.9	180.0	175.5	174.0	170.2	165.7	161.1
72.5°	134.6	152.8	153.6	153.6	149.0	149.0	144.5	142.2	142.2	137.7	132.4
75°	99.1	111.2	112.7	114.2	116.5	118.8	115.7	115.7	115.0	110.4	108.2
77.5°	65.8	76.4	80.2	85.5	88.5	88.5	90.0	91.5	90.0	87.7	86.2
80°	42.4	49.9	54.5	57.5	62.0	64.3	66.6	67.3	65.8	65.1	62.8
82.5°	28.0	30.3	32.5	36.3	41.6	45.4	45.4	44.6	46.1	45.4	44.6
85°	15.9	17.4	18.2	18.9	21.9	25.7	26.5	27.2	28.7	27.2	25.7
87.5°	6.1	6.8	6.8	6.8	8.3	9.1	11.3	14.4	13.6	12.1	12.1
90°	8.7	7.0	6.2	5.6	4.3	3.1	1.8	0.6	1.8	3.1	4.3
92.5°	21.5	20.8	20.4	20.0	19.3	18.5	17.8	17.0	17.8	18.5	19.3
95°	38.9	37.9	37.4	37.0	36.1	35.2	34.3	33.4	34.3	35.2	36.1
97.5°	58.9	58.2	57.8	57.5	56.9	56.2	55.6	55.0	55.6	56.2	56.9
100°	81.4	80.8	80.5	80.1	79.4	78.6	77.9	77.1	77.9	78.6	79.4
102.5°	105.6	104.7	104.3	104.1	103.7	103.4	103.0	102.6	103.0	103.4	103.7
105°	130.3	129.2	128.6	128.5	128.2	128.0	127.7	127.5	127.7	128.0	128.2
107.5°	158.3	157.8	157.5	157.4	157.3	157.2	157.0	156.9	157.0	157.2	157.3
110°	185.7	185.4	185.3	185.2	184.9	184.6	184.4	184.1	184.4	184.6	184.9

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	213.0	213.0	213.0	212.9	212.8	212.7	212.6	212.5	212.6	212.7	212.8
115°	242.1	242.4	242.5	242.3	241.9	241.6	241.2	240.8	241.2	241.6	241.9
117.5°	269.9	270.2	270.3	270.2	270.1	270.0	269.8	269.7	269.8	270.0	270.1
120°	298.8	299.4	299.7	299.3	298.6	297.8	297.1	296.3	297.1	297.8	298.6
122.5°	326.0	326.3	326.4	326.1	325.6	325.1	324.6	324.1	324.6	325.1	325.6
125°	353.7	354.0	354.1	353.9	353.5	353.2	352.8	352.4	352.8	353.2	353.5
127.5°	381.5	381.8	381.9	381.5	380.8	380.0	379.3	378.5	379.3	380.0	380.8
130°	408.5	408.9	409.1	408.6	407.6	406.5	405.5	404.5	405.5	406.5	407.6
132.5°	434.7	435.0	435.1	434.6	433.6	432.6	431.6	430.6	431.6	432.6	433.6
135°	460.4	460.5	460.6	460.2	459.5	458.7	458.0	457.2	458.0	458.7	459.5
137.5°	485.0	484.6	484.4	484.1	483.5	482.8	482.2	481.6	482.2	482.8	483.5
140°	510.1	510.0	509.9	509.6	509.0	508.3	507.7	507.1	507.7	508.3	509.0
142.5°	533.6	533.3	533.2	532.9	532.2	531.6	530.9	530.3	530.9	531.6	532.2
145°	556.4	556.0	555.8	555.7	555.4	555.2	554.9	554.7	554.9	555.2	555.4
147.5°	578.5	578.1	577.9	577.6	577.1	576.6	576.1	575.6	576.1	576.6	577.1
150°	599.3	599.0	598.9	598.8	598.5	598.2	598.0	597.7	598.0	598.2	598.5
152.5°	617.8	617.7	617.6	617.4	617.0	616.7	616.3	615.9	616.3	616.7	617.0
155°	635.3	635.2	635.1	635.1	635.1	635.1	635.1	635.1	635.1	635.1	635.1
157.5°	651.2	651.1	651.0	651.1	651.2	651.3	651.5	651.6	651.5	651.3	651.2
160°	665.7	665.7	665.7	665.8	666.1	666.4	666.6	666.9	666.6	666.4	666.1
162.5°	679.0	678.9	678.8	679.0	679.4	679.7	680.1	680.5	680.1	679.7	679.4
165°	690.1	690.1	690.1	690.3	690.7	691.0	691.4	691.8	691.4	691.0	690.7
167.5°	699.4	699.3	699.2	699.4	699.9	700.4	700.9	701.4	700.9	700.4	699.9
170°	707.1	707.1	707.1	707.4	707.9	708.4	708.9	709.4	708.9	708.4	707.9
172.5°	713.3	713.3	713.3	713.6	714.1	714.6	715.1	715.6	715.1	714.6	714.1
175°	717.3	717.3	717.3	717.6	718.1	718.6	719.1	719.6	719.1	718.6	718.1
177.5°	719.6	719.6	719.6	719.8	720.3	720.8	721.3	721.8	721.3	720.8	720.3
180°	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	872.2	868.4	866.9	863.1	854.0	848.0	841.2	836.6	837.4	833.6	835.9
5°	844.9	844.2	838.9	831.3	818.5	811.7	799.6	793.5	790.5	791.2	786.7
7.5°	822.2	815.4	811.7	799.6	787.4	773.1	763.2	757.9	753.4	748.9	745.8
10°	796.5	790.5	784.4	771.6	754.9	741.3	727.7	722.4	715.6	712.6	710.3
12.5°	769.3	765.5	757.9	742.8	723.9	711.0	695.2	692.1	683.1	677.0	675.5
15°	744.3	742.1	728.4	711.0	692.1	679.3	665.7	656.6	641.5	644.5	639.2
17.5°	717.9	708.0	699.7	676.3	667.2	647.5	631.6	627.1	616.5	609.7	602.9
20°	688.4	682.3	671.7	656.6	634.6	612.0	599.9	592.3	586.2	575.6	572.6
22.5°	660.4	652.8	643.7	624.1	605.1	586.2	569.6	562.8	555.2	547.7	543.1
25°	638.4	627.1	617.2	593.0	574.1	558.2	547.7	536.3	525.7	521.2	519.7
27.5°	604.4	597.6	587.7	565.1	547.7	530.3	520.4	512.9	501.5	496.2	491.7
30°	582.5	568.8	557.5	539.3	521.9	503.0	494.0	484.9	478.1	471.3	466.0
32.5°	553.0	542.4	533.3	515.1	497.7	480.3	470.5	456.9	453.1	447.8	441.8
35°	524.2	517.4	507.6	487.9	469.0	456.9	446.3	433.4	428.9	425.1	419.8
37.5°	497.0	487.1	480.3	461.4	444.8	430.4	422.1	411.5	408.5	403.9	400.2
40°	473.5	463.7	456.9	438.0	420.6	405.4	400.2	389.6	385.0	379.7	377.5
42.5°	447.1	438.7	429.7	416.0	397.9	382.8	372.2	366.1	360.1	357.8	353.3
45°	419.1	411.5	404.7	389.6	370.7	360.1	351.0	342.7	338.1	334.3	331.3
47.5°	394.9	388.1	379.0	362.3	347.2	337.4	328.3	320.0	315.4	310.9	307.1
50°	366.9	363.1	353.3	337.4	323.0	311.7	303.3	295.8	292.7	287.4	281.4
52.5°	341.9	335.1	326.8	313.9	301.1	287.4	276.1	271.6	266.3	263.2	257.9
55°	312.4	307.9	298.8	287.4	273.8	262.5	254.2	248.1	241.3	238.3	231.5
57.5°	287.4	279.1	274.6	260.2	247.4	236.0	230.0	223.9	216.3	211.8	208.8
60°	260.2	252.6	245.8	233.7	224.7	212.6	203.5	198.2	192.9	186.8	183.8
62.5°	233.7	227.7	219.4	209.5	198.2	188.4	181.5	174.0	171.0	164.9	162.6
65°	205.0	200.5	193.6	182.3	173.2	164.9	158.1	152.0	149.0	146.7	145.2
67.5°	179.3	173.2	168.7	158.9	149.0	142.2	138.4	134.6	130.9	128.6	126.3
70°	152.8	148.3	143.7	134.6	127.8	121.8	118.8	115.7	113.5	111.2	108.9
72.5°	125.6	123.3	118.8	112.7	107.4	102.9	100.6	96.8	94.6	90.8	89.3
75°	103.6	99.8	97.6	92.3	87.7	84.0	80.9	76.4	73.4	71.9	71.1
77.5°	81.7	80.2	77.2	72.6	70.3	66.6	62.0	60.5	59.0	59.0	58.2
80°	61.3	59.0	56.7	53.0	50.7	47.7	47.7	47.7	46.9	47.7	46.9
82.5°	41.6	40.1	38.6	36.3	35.6	35.6	36.3	36.3	36.3	36.3	36.3
85°	24.2	24.2	24.2	25.0	24.2	24.2	25.0	25.7	25.0	25.0	24.2
87.5°	11.3	11.3	12.1	12.1	12.9	12.9	12.9	12.9	12.9	12.9	13.6
90°	5.6	6.2	7.0	8.7	10.3	12.0	13.6	14.1	14.6	15.1	15.6
92.5°	20.0	20.4	20.8	21.5	22.3	23.0	23.8	24.2	24.6	24.9	25.3
95°	37.0	37.4	37.9	38.9	39.9	40.9	41.9	42.4	42.9	43.4	43.9
97.5°	57.5	57.8	58.2	58.9	59.7	60.4	61.2	61.8	62.4	63.1	63.7
100°	80.1	80.5	80.8	81.4	82.1	82.7	83.3	83.7	84.1	84.4	84.8
102.5°	104.1	104.3	104.7	105.6	106.5	107.3	108.2	108.6	109.0	109.3	109.7
105°	128.5	128.6	129.2	130.3	131.4	132.6	133.7	133.7	133.7	133.7	133.7
107.5°	157.4	157.5	157.8	158.3	158.8	159.3	159.8	160.2	160.6	160.9	161.3
110°	185.2	185.3	185.4	185.7	185.9	186.2	186.4	186.9	187.4	187.9	188.4

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	212.9	213.0	213.0	213.0	213.0	213.0	213.0	213.6	214.3	214.9	215.6
115°	242.3	242.5	242.4	242.1	241.9	241.6	241.4	241.5	241.6	241.7	241.8
117.5°	270.2	270.3	270.2	269.9	269.6	269.4	269.1	269.1	269.1	269.1	269.1
120°	299.3	299.7	299.4	298.8	298.1	297.5	296.9	296.8	296.6	296.5	296.4
122.5°	326.1	326.4	326.3	326.0	325.7	325.5	325.2	324.8	324.4	324.1	323.7
125°	353.9	354.1	354.0	353.7	353.5	353.2	353.0	352.5	352.0	351.5	351.0
127.5°	381.5	381.9	381.8	381.5	381.2	381.0	380.7	379.9	379.2	378.4	377.7
130°	408.6	409.1	408.9	408.5	408.2	407.8	407.4	406.9	406.4	405.9	405.4
132.5°	434.6	435.1	435.0	434.7	434.5	434.2	434.0	433.4	432.8	432.1	431.5
135°	460.2	460.6	460.5	460.4	460.3	460.2	460.1	459.6	459.1	458.6	458.1
137.5°	484.1	484.4	484.6	485.0	485.3	485.7	486.1	485.5	484.9	484.2	483.6
140°	509.6	509.9	510.0	510.1	510.2	510.4	510.5	510.4	510.2	510.1	510.0
142.5°	532.9	533.2	533.3	533.6	533.8	534.1	534.3	534.2	534.0	533.9	533.8
145°	555.7	555.8	556.0	556.4	556.7	557.1	557.5	557.4	557.2	557.1	557.0
147.5°	577.6	577.9	578.1	578.5	578.8	579.2	579.6	579.6	579.6	579.6	579.6
150°	598.8	598.9	599.0	599.3	599.5	599.8	600.0	600.0	600.0	600.0	600.0
152.5°	617.4	617.6	617.7	617.8	617.9	618.0	618.1	618.4	618.6	618.9	619.2
155°	635.1	635.1	635.2	635.3	635.4	635.6	635.7	636.2	636.7	637.2	637.7
157.5°	651.1	651.0	651.1	651.2	651.3	651.5	651.6	652.1	652.6	653.1	653.6
160°	665.8	665.7	665.7	665.7	665.7	665.7	665.7	666.3	667.0	667.6	668.3
162.5°	679.0	678.8	678.9	679.0	679.1	679.2	679.3	679.9	680.6	681.2	681.9
165°	690.3	690.1	690.1	690.1	690.1	690.1	690.1	690.9	691.6	692.4	693.1
167.5°	699.4	699.2	699.3	699.4	699.5	699.6	699.7	700.5	701.2	702.0	702.7
170°	707.4	707.1	707.1	707.1	707.1	707.1	707.1	708.0	708.9	709.8	710.7
172.5°	713.6	713.3	713.3	713.3	713.3	713.3	713.3	714.1	714.8	715.6	716.3
175°	717.6	717.3	717.3	717.3	717.3	717.3	717.3	718.1	718.8	719.6	720.3
177.5°	719.8	719.6	719.6	719.6	719.6	719.6	719.6	720.4	721.1	721.9	722.6
180°	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.1	835.9	833.6	829.1	828.3	829.8	834.3	832.8	829.1	835.9	829.8
5°	789.0	785.2	783.7	785.2	780.6	778.4	782.9	780.6	782.9	783.7	785.9
7.5°	744.3	745.1	740.5	741.3	735.3	736.8	736.8	736.8	739.0	740.5	743.6
10°	705.8	707.3	702.0	702.7	698.2	695.2	697.4	702.0	702.0	702.0	703.5
12.5°	674.7	667.9	664.1	663.4	658.1	656.6	661.1	662.6	666.4	666.4	668.7
15°	636.2	634.6	631.6	631.6	618.8	621.8	623.3	628.6	636.2	630.1	631.6
17.5°	601.4	597.6	593.8	592.3	590.8	586.2	592.3	591.5	596.1	596.8	599.1
20°	570.4	567.3	559.8	560.5	562.0	555.2	559.0	559.0	563.5	568.1	573.4
22.5°	540.1	537.1	533.3	534.8	530.3	528.7	528.7	532.5	537.8	541.6	540.9
25°	516.6	511.3	509.1	506.8	504.5	506.1	503.8	507.6	511.3	513.6	511.3
27.5°	490.2	487.9	483.4	481.1	477.3	478.8	480.3	483.4	485.6	485.6	487.9
30°	464.5	461.4	459.9	457.6	457.6	454.6	455.4	458.4	460.7	462.9	466.0
32.5°	439.5	437.2	434.9	434.9	433.4	432.7	431.9	436.5	436.5	441.0	441.0
35°	419.1	415.3	415.3	411.5	413.0	412.3	410.7	413.8	414.5	417.6	416.8
37.5°	396.4	396.4	394.9	391.1	388.1	388.8	392.6	392.6	394.9	394.1	396.4
40°	373.7	372.2	372.2	369.9	369.1	368.4	369.1	369.9	373.7	372.9	373.7
42.5°	351.0	351.7	348.0	348.0	348.0	345.7	346.4	347.2	348.7	350.2	352.5
45°	329.0	327.5	326.8	325.3	323.8	324.5	323.8	326.8	326.0	327.5	329.8
47.5°	305.6	303.3	302.6	299.5	299.5	301.1	300.3	302.6	303.3	305.6	304.1
50°	282.9	279.9	277.6	278.4	273.8	275.3	275.3	277.6	279.9	280.6	282.1
52.5°	256.4	255.7	254.9	251.1	250.4	249.6	250.4	251.1	254.2	256.4	257.2
55°	230.7	230.0	225.4	223.9	221.6	221.6	223.1	223.9	229.2	230.0	233.0
57.5°	207.3	205.0	199.7	198.9	198.9	198.9	196.7	199.7	201.2	205.0	205.0
60°	181.5	181.5	177.0	177.0	177.8	177.0	177.0	177.8	177.8	180.8	182.3
62.5°	161.1	160.4	160.4	158.9	158.1	158.9	158.1	158.1	158.9	161.1	163.4
65°	143.0	142.2	141.5	140.7	139.2	139.2	139.9	141.5	141.5	143.0	143.7
67.5°	125.6	125.6	124.1	124.1	123.3	122.5	123.3	122.5	125.6	125.6	126.3
70°	108.2	107.4	105.1	104.4	102.1	102.9	102.9	105.1	105.9	107.4	108.9
72.5°	87.0	87.0	85.5	84.0	84.7	83.2	83.2	84.0	84.0	86.2	87.0
75°	71.9	70.3	69.6	70.3	69.6	71.1	69.6	69.6	71.1	71.1	71.1
77.5°	59.0	59.0	58.2	58.2	59.0	58.2	59.0	59.0	59.0	58.2	59.0
80°	48.4	47.7	47.7	47.7	46.9	46.9	46.9	46.9	46.9	46.9	46.9
82.5°	36.3	36.3	35.6	36.3	36.3	35.6	36.3	35.6	35.6	36.3	36.3
85°	24.2	25.7	24.2	24.2	25.0	25.0	25.7	25.0	25.7	24.2	25.0
87.5°	12.9	13.6	13.6	12.9	12.9	13.6	13.6	13.6	14.4	12.9	13.6
90°	15.9	16.0	16.3	16.5	16.8	17.0	16.8	16.5	16.3	16.0	15.9
92.5°	25.5	25.4	25.1	24.9	24.6	24.4	24.6	24.9	25.1	25.4	25.5
95°	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.2
97.5°	64.0	63.9	63.8	63.7	63.6	63.5	63.6	63.7	63.8	63.9	64.0
100°	85.0	85.1	85.4	85.6	85.9	86.1	85.9	85.6	85.4	85.1	85.0
102.5°	109.9	109.8	109.7	109.6	109.5	109.4	109.5	109.6	109.7	109.8	109.9
105°	133.7	133.8	134.1	134.3	134.6	134.8	134.6	134.3	134.1	133.8	133.7
107.5°	161.5	161.4	161.3	161.2	161.0	160.9	161.0	161.2	161.3	161.4	161.5
110°	188.7	188.6	188.3	188.0	187.8	187.5	187.8	188.0	188.3	188.6	188.7

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	215.9	215.9	215.9	215.9	215.9	215.9	215.9	215.9	215.9	215.9	215.9
115°	241.9	241.8	241.7	241.6	241.5	241.4	241.5	241.6	241.7	241.8	241.9
117.5°	269.1	268.9	268.5	268.2	267.8	267.4	267.8	268.2	268.5	268.9	269.1
120°	296.3	296.2	295.9	295.7	295.4	295.2	295.4	295.7	295.9	296.2	296.3
122.5°	323.5	323.3	322.9	322.6	322.2	321.8	322.2	322.6	322.9	323.3	323.5
125°	350.7	350.4	349.9	349.4	348.9	348.4	348.9	349.4	349.9	350.4	350.7
127.5°	377.3	377.1	376.6	376.1	375.6	375.1	375.6	376.1	376.6	377.1	377.3
130°	405.1	404.7	403.8	402.9	402.0	401.1	402.0	402.9	403.8	404.7	405.1
132.5°	431.2	430.9	430.2	429.6	428.9	428.3	428.9	429.6	430.2	430.9	431.2
135°	457.8	457.7	457.4	457.2	456.9	456.7	456.9	457.2	457.4	457.7	457.8
137.5°	483.3	483.1	482.7	482.4	482.0	481.6	482.0	482.4	482.7	483.1	483.3
140°	509.9	509.5	508.6	507.7	506.9	506.0	506.9	507.7	508.6	509.5	509.9
142.5°	533.7	533.4	532.8	532.1	531.5	530.9	531.5	532.1	532.8	533.4	533.7
145°	556.9	556.7	556.2	555.7	555.2	554.7	555.2	555.7	556.2	556.7	556.9
147.5°	579.6	579.2	578.5	577.7	577.0	576.2	577.0	577.7	578.5	579.2	579.6
150°	600.0	599.6	598.9	598.1	597.4	596.6	597.4	598.1	598.9	599.6	600.0
152.5°	619.3	619.0	618.3	617.7	617.0	616.4	617.0	617.7	618.3	619.0	619.3
155°	638.0	637.6	636.7	635.8	634.9	634.0	634.9	635.8	636.7	637.6	638.0
157.5°	653.8	653.4	652.7	651.9	651.2	650.4	651.2	651.9	652.7	653.4	653.8
160°	668.6	668.3	667.8	667.3	666.8	666.3	666.8	667.3	667.8	668.3	668.6
162.5°	682.2	681.8	680.9	680.0	679.1	678.2	679.1	680.0	680.9	681.8	682.2
165°	693.5	693.1	692.2	691.3	690.4	689.5	690.4	691.3	692.2	693.1	693.5
167.5°	703.1	702.7	702.0	701.2	700.5	699.7	700.5	701.2	702.0	702.7	703.1
170°	711.1	710.7	709.8	708.9	708.0	707.1	708.0	708.9	709.8	710.7	711.1
172.5°	716.7	716.3	715.4	714.5	713.7	712.8	713.7	714.5	715.4	716.3	716.7
175°	720.7	720.3	719.4	718.5	717.6	716.7	717.6	718.5	719.4	720.3	720.7
177.5°	723.0	722.6	721.7	720.8	719.9	719.0	719.9	720.8	721.7	722.6	723.0
180°	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.9	838.9	835.9	829.8	835.9	839.6	843.4	849.5	852.5	852.5	857.0
5°	788.2	794.3	792.0	790.5	796.5	800.3	806.4	813.9	822.2	827.5	833.6
7.5°	745.8	749.6	753.4	753.4	759.5	767.8	776.9	785.9	796.5	804.1	808.6
10°	708.8	711.8	714.1	717.1	726.2	735.3	747.4	758.7	767.8	776.1	783.7
12.5°	673.2	677.8	683.1	685.3	692.1	703.5	714.8	728.4	742.8	751.1	758.7
15°	639.2	641.5	647.5	654.3	660.4	672.5	686.8	701.2	713.3	726.2	733.0
17.5°	604.4	605.1	621.0	617.2	636.9	648.3	655.8	669.4	689.1	699.7	710.3
20°	570.4	577.9	584.7	588.5	599.1	612.0	633.9	644.5	660.4	670.2	679.3
22.5°	543.9	555.2	555.2	564.3	569.6	581.7	597.6	618.0	635.4	642.2	655.1
25°	520.4	525.7	534.8	537.8	547.7	558.2	568.8	590.8	609.7	618.8	627.8
27.5°	490.2	497.0	509.1	509.1	521.9	533.3	546.1	560.5	579.4	592.3	602.1
30°	466.7	473.5	478.8	487.1	492.4	503.0	525.7	536.3	553.0	564.3	576.4
32.5°	444.8	450.1	454.6	463.7	469.7	481.8	494.0	512.9	527.2	537.8	550.7
35°	420.6	425.9	431.9	438.7	447.8	459.2	470.5	486.4	500.8	510.6	521.2
37.5°	397.9	401.7	410.7	415.3	422.8	433.4	447.8	464.5	477.3	484.9	495.5
40°	375.9	379.0	385.8	394.1	399.4	407.7	422.8	437.2	453.1	462.2	470.5
42.5°	352.5	356.3	362.3	370.7	379.0	388.1	396.4	413.0	427.4	434.9	444.0
45°	332.1	334.3	338.9	347.2	355.5	362.3	375.2	390.3	403.9	410.0	419.8
47.5°	307.9	310.1	316.9	320.7	329.8	338.9	351.7	366.9	379.0	385.0	394.1
50°	282.9	285.2	289.7	298.0	304.1	313.9	325.3	338.1	353.3	361.6	366.9
52.5°	258.7	263.2	267.0	273.8	281.4	291.2	301.8	313.9	326.8	335.1	341.2
55°	234.5	238.3	242.8	246.6	255.7	264.8	276.9	288.2	299.5	307.1	313.9
57.5°	207.3	212.6	217.1	224.7	231.5	239.0	252.6	261.7	275.3	280.6	286.7
60°	183.8	189.1	192.9	198.9	205.0	214.8	223.9	235.3	246.6	253.4	261.0
62.5°	164.1	166.4	168.7	174.7	180.8	189.9	198.9	210.3	222.4	226.2	232.2
65°	144.5	146.7	150.5	155.8	160.4	165.7	175.5	184.6	195.9	202.0	204.2
67.5°	127.8	130.1	130.9	134.6	138.4	144.5	149.8	158.9	169.4	173.2	177.8
70°	108.9	112.7	113.5	116.5	118.0	121.8	127.8	134.6	143.0	149.8	153.6
72.5°	87.0	92.3	93.8	98.3	100.6	104.4	108.9	114.2	119.5	122.5	125.6
75°	71.1	72.6	73.4	77.2	80.9	86.2	88.5	91.5	96.1	99.8	102.9
77.5°	59.0	59.8	60.5	60.5	61.3	64.3	68.8	72.6	75.6	77.2	79.4
80°	47.7	46.9	46.9	47.7	47.7	47.7	49.2	54.5	56.0	59.8	59.0
82.5°	37.1	35.6	36.3	35.6	35.6	35.6	35.6	36.3	36.3	38.6	40.1
85°	24.2	25.0	24.2	24.2	23.4	24.2	23.4	23.4	22.7	22.7	21.9
87.5°	12.9	13.6	12.9	12.9	12.1	12.9	12.1	12.1	11.3	11.3	9.8
90°	15.6	15.1	14.6	14.1	13.6	12.0	10.3	8.7	7.0	6.2	5.6
92.5°	25.3	24.9	24.6	24.2	23.8	23.0	22.3	21.5	20.8	20.4	20.0
95°	43.9	43.4	42.9	42.4	41.9	40.9	39.9	38.9	37.9	37.4	37.0
97.5°	63.7	63.1	62.4	61.8	61.2	60.4	59.7	58.9	58.2	57.8	57.5
100°	84.8	84.4	84.1	83.7	83.3	82.7	82.1	81.4	80.8	80.5	80.1
102.5°	109.7	109.3	109.0	108.6	108.2	107.3	106.5	105.6	104.7	104.3	104.1
105°	133.7	133.7	133.7	133.7	133.7	132.6	131.4	130.3	129.2	128.6	128.5
107.5°	161.3	160.9	160.6	160.2	159.8	159.3	158.8	158.3	157.8	157.5	157.4
110°	188.4	187.9	187.4	186.9	186.4	186.2	185.9	185.7	185.4	185.3	185.2

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	215.6	214.9	214.3	213.6	213.0	213.0	213.0	213.0	213.0	213.0	212.9
115°	241.8	241.7	241.6	241.5	241.4	241.6	241.9	242.1	242.4	242.5	242.3
117.5°	269.1	269.1	269.1	269.1	269.1	269.4	269.6	269.9	270.2	270.3	270.2
120°	296.4	296.5	296.6	296.8	296.9	297.5	298.1	298.8	299.4	299.7	299.3
122.5°	323.7	324.1	324.4	324.8	325.2	325.5	325.7	326.0	326.3	326.4	326.1
125°	351.0	351.5	352.0	352.5	353.0	353.2	353.5	353.7	354.0	354.1	353.9
127.5°	377.7	378.4	379.2	379.9	380.7	381.0	381.2	381.5	381.8	381.9	381.5
130°	405.4	405.9	406.4	406.9	407.4	407.8	408.2	408.5	408.9	409.1	408.6
132.5°	431.5	432.1	432.8	433.4	434.0	434.2	434.5	434.7	435.0	435.1	434.6
135°	458.1	458.6	459.1	459.6	460.1	460.2	460.3	460.4	460.5	460.6	460.2
137.5°	483.6	484.2	484.9	485.5	486.1	485.7	485.3	485.0	484.6	484.4	484.1
140°	510.0	510.1	510.2	510.4	510.5	510.4	510.2	510.1	510.0	509.9	509.6
142.5°	533.8	533.9	534.0	534.2	534.3	534.1	533.8	533.6	533.3	533.2	532.9
145°	557.0	557.1	557.2	557.4	557.5	557.1	556.7	556.4	556.0	555.8	555.7
147.5°	579.6	579.6	579.6	579.6	579.6	579.2	578.8	578.5	578.1	577.9	577.6
150°	600.0	600.0	600.0	600.0	600.0	599.8	599.5	599.3	599.0	598.9	598.8
152.5°	619.2	618.9	618.6	618.4	618.1	618.0	617.9	617.8	617.7	617.6	617.4
155°	637.7	637.2	636.7	636.2	635.7	635.6	635.4	635.3	635.2	635.1	635.1
157.5°	653.6	653.1	652.6	652.1	651.6	651.5	651.3	651.2	651.1	651.0	651.1
160°	668.3	667.6	667.0	666.3	665.7	665.7	665.7	665.7	665.7	665.7	665.8
162.5°	681.9	681.2	680.6	679.9	679.3	679.2	679.1	679.0	678.9	678.8	679.0
165°	693.1	692.4	691.6	690.9	690.1	690.1	690.1	690.1	690.1	690.1	690.3
167.5°	702.7	702.0	701.2	700.5	699.7	699.6	699.5	699.4	699.3	699.2	699.4
170°	710.7	709.8	708.9	708.0	707.1	707.1	707.1	707.1	707.1	707.1	707.4
172.5°	716.3	715.6	714.8	714.1	713.3	713.3	713.3	713.3	713.3	713.3	713.6
175°	720.3	719.6	718.8	718.1	717.3	717.3	717.3	717.3	717.3	717.3	717.6
177.5°	722.6	721.9	721.1	720.4	719.6	719.6	719.6	719.6	719.6	719.6	719.8
180°	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3	721.3

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	883.5	883.5	883.5	883.5
2.5°	860.8	866.1	876.7	885.8
5°	842.7	851.0	866.9	882.8
7.5°	820.7	833.6	854.0	876.0
10°	799.6	816.2	841.2	866.9
12.5°	778.4	795.8	822.2	855.5
15°	753.4	771.6	803.3	843.4
17.5°	731.5	755.7	784.4	824.5
20°	708.0	726.2	763.2	805.6
22.5°	678.5	708.8	743.6	788.2
25°	655.1	681.5	716.3	767.0
27.5°	626.3	657.3	699.7	744.3
30°	602.9	628.6	667.9	721.6
32.5°	575.6	605.9	646.8	699.7
35°	551.4	577.2	615.7	669.4
37.5°	522.7	550.7	593.8	641.5
40°	497.7	525.0	565.8	610.4
42.5°	467.5	496.2	537.1	574.9
45°	443.3	469.7	502.3	537.1
47.5°	413.8	441.8	473.5	497.7
50°	387.3	413.0	438.0	458.4
52.5°	358.5	382.0	404.7	419.8
55°	332.1	350.2	368.4	379.0
57.5°	301.1	318.5	333.6	339.6
60°	273.8	288.2	298.0	304.8
62.5°	245.1	255.7	263.2	267.0
65°	217.1	224.7	228.4	232.2
67.5°	188.4	195.2	197.4	202.0
70°	158.1	165.7	167.2	169.4
72.5°	135.4	135.4	138.4	141.5
75°	108.2	109.7	111.2	111.2
77.5°	84.7	84.7	86.2	87.0
80°	62.0	62.8	62.8	62.0
82.5°	42.4	43.9	42.4	41.6
85°	23.4	26.5	25.0	25.0
87.5°	9.8	9.8	11.3	9.8
90°	4.3	3.1	1.8	0.6
92.5°	19.3	18.5	17.8	17.0
95°	36.1	35.2	34.3	33.4
97.5°	56.9	56.2	55.6	55.0
100°	79.4	78.6	77.9	77.1
102.5°	103.7	103.4	103.0	102.6
105°	128.2	128.0	127.7	127.5
107.5°	157.3	157.2	157.0	156.9
110°	184.9	184.6	184.4	184.1

TEST NUMBER: P1012642

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	212.8	212.7	212.6	212.5
115°	241.9	241.6	241.2	240.8
117.5°	270.1	270.0	269.8	269.7
120°	298.6	297.8	297.1	296.3
122.5°	325.6	325.1	324.6	324.1
125°	353.5	353.2	352.8	352.4
127.5°	380.8	380.0	379.3	378.5
130°	407.6	406.5	405.5	404.5
132.5°	433.6	432.6	431.6	430.6
135°	459.5	458.7	458.0	457.2
137.5°	483.5	482.8	482.2	481.6
140°	509.0	508.3	507.7	507.1
142.5°	532.2	531.6	530.9	530.3
145°	555.4	555.2	554.9	554.7
147.5°	577.1	576.6	576.1	575.6
150°	598.5	598.2	598.0	597.7
152.5°	617.0	616.7	616.3	615.9
155°	635.1	635.1	635.1	635.1
157.5°	651.2	651.3	651.5	651.6
160°	666.1	666.4	666.6	666.9
162.5°	679.4	679.7	680.1	680.5
165°	690.7	691.0	691.4	691.8
167.5°	699.9	700.4	700.9	701.4
170°	707.9	708.4	708.9	709.4
172.5°	714.1	714.6	715.1	715.6
175°	718.1	718.6	719.1	719.6
177.5°	720.3	720.8	721.3	721.8
180°	721.3	721.3	721.3	721.3

(END OF REPORT)