

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012643

Luminaire Tested: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012643
REPORT IS A COMBINATION OF REPORTS P993441 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D585UB27-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4307.0 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	99	95	91	88	91	88	84	82	74	72	70	62	61	59	51	50	49
2	90	83	77	73	83	77	72	68	66	62	59	56	53	51	46	44	43
3	83	74	67	61	76	69	62	57	59	54	50	50	46	44	41	39	37
4	76	66	58	52	70	61	54	49	53	47	43	45	41	38	37	35	32
5	70	59	51	45	65	55	48	43	47	42	38	40	36	33	34	31	28
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25
7	60	48	40	35	55	45	38	33	39	34	30	33	29	26	28	25	23
8	56	44	36	31	51	41	34	29	36	30	26	31	27	23	26	23	20
9	52	40	33	28	48	37	31	26	33	27	24	28	24	21	24	21	19
10	49	37	30	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9510	9510	9510	9510
5°	9518	10953	9542	8126
10°	9434	13222	9475	7098
15°	9336	15006	9336	6258
20°	9145	16186	9196	5551
25°	9004	15378	8987	5066
30°	8841	10655	8823	4590
35°	8645	6841	8606	4232
40°	8401	4831	8359	3876
45°	7977	3865	7965	3528
50°	7454	3234	7430	3122
55°	6867	2665	6811	2647
60°	6289	2203	6227	2251
65°	5613	1763	5649	1908
70°	4989	1225	5124	1543
75°	4230	909	4401	1186
80°	3366	603	3654	889
85°	2401	286	2613	554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 12696 cd/sqm

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	2.0
10°-20°	271.6	6.3
20°-30°	427.8	9.9
30°-40°	444.8	10.3
40°-50°	380.6	8.8
50°-60°	290.1	6.7
60°-70°	185.9	4.3
70°-80°	89.1	2.1
80°-90°	25.0	0.6
90°-100°	151.9	3.5
100°-110°	444.7	10.3
110°-120°	434.2	10.1
120°-130°	345.8	8.0
130°-140°	272.8	6.3
140°-150°	203.5	4.7
150°-160°	141.9	3.3
160°-170°	83.4	1.9
170°-180°	27.1	0.6
0°-30°	786.1	18.3
0°-40°	1231.0	28.6
0°-60°	1901.6	44.2
0°-90°	2201.6	51.1
90°-120°	1030.8	23.9
90°-150°	1853.0	43.0
90°-180°	2105.0	48.9
0°-180°	4307.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	884	884	884	884	884	
5°	883	1049	885	778	883	84
15°	843	1491	843	622	843	237
25°	767	1536	766	506	767	353
35°	669	666	666	412	669	419
45°	537	356	536	324	537	414
55°	379	223	376	222	379	340
65°	232	129	234	139	232	232
75°	111	54	116	71	111	120
85°	25	13	27	25	25	28
90°	1	16	1	16	1	3
95°	19	66	19	66	19	20
105°	66	721	66	721	66	70
115°	116	876	116	876	116	115
125°	162	691	162	691	162	143
135°	189	560	189	560	189	146
145°	216	438	216	438	216	135
155°	245	363	245	363	245	113
165°	268	317	268	317	268	76
175°	279	285	279	285	279	27
180°	280	280	280	280	280	

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	885.8	891.8	896.4	899.4	907.0	911.5	915.3	922.1	922.1	923.6	926.6
5°	882.8	895.6	904.7	916.8	932.7	940.2	950.8	959.9	972.8	979.6	986.4
7.5°	876.0	894.1	913.0	931.2	954.6	969.7	980.3	1003.8	1020.4	1040.9	1056.7
10°	866.9	891.8	916.0	944.0	975.8	998.5	1014.4	1045.4	1077.2	1105.9	1130.1
12.5°	855.5	885.8	920.6	954.6	999.2	1021.9	1047.7	1086.2	1131.6	1167.9	1200.5
15°	843.4	878.2	917.6	959.2	1015.1	1046.9	1084.0	1130.9	1181.5	1233.7	1278.4
17.5°	824.5	868.4	912.3	972.8	1038.6	1057.5	1089.3	1153.6	1216.3	1263.2	1317.7
20°	805.6	854.8	910.0	964.5	1035.6	1079.4	1108.9	1177.0	1244.3	1301.1	1353.3
22.5°	788.2	839.6	897.1	966.0	1032.5	1076.4	1113.5	1184.6	1262.5	1326.0	1390.3
25°	767.0	823.0	886.5	951.6	1032.5	1065.8	1106.7	1189.1	1271.6	1344.9	1424.4
27.5°	744.3	801.1	863.8	930.4	1004.5	1053.7	1093.8	1182.3	1282.9	1361.6	1443.3
30°	721.6	779.9	840.4	900.2	983.4	1030.3	1076.4	1174.0	1289.0	1379.0	1441.8
32.5°	699.7	748.9	808.6	866.9	949.3	1000.8	1053.0	1165.7	1291.2	1366.9	1397.1
35°	669.4	720.9	769.3	831.3	914.5	965.2	1026.5	1164.9	1281.4	1328.3	1313.2
37.5°	641.5	684.6	730.7	785.9	871.4	937.2	1000.8	1145.2	1248.9	1251.9	1166.4
40°	610.4	646.0	684.6	742.8	835.1	900.2	969.0	1115.0	1189.9	1145.2	994.7
42.5°	574.9	606.7	636.9	693.6	794.3	866.9	941.0	1077.2	1104.4	1001.5	844.9
45°	537.1	562.8	590.8	650.5	751.1	823.0	897.1	1018.9	990.9	845.7	696.7
47.5°	497.7	519.7	546.9	601.4	705.0	778.4	848.7	935.7	864.6	708.8	584.0
50°	458.4	475.8	502.3	558.2	658.1	724.7	789.7	846.4	746.6	608.2	482.6
52.5°	419.8	433.4	460.7	508.3	605.1	668.7	715.6	737.5	636.2	502.3	419.1
55°	379.0	394.1	412.3	460.7	556.7	603.6	634.6	633.9	529.5	425.9	346.4
57.5°	339.6	353.3	369.1	417.6	495.5	527.2	553.7	540.9	441.8	348.7	297.3
60°	304.8	312.4	329.8	370.7	429.7	456.9	472.0	450.1	360.8	294.3	245.8
62.5°	267.0	274.6	289.0	327.5	363.8	378.2	391.1	363.1	298.0	239.8	210.3
65°	232.2	242.1	251.1	282.1	301.8	319.2	317.7	294.3	233.0	195.2	171.0
67.5°	202.0	205.7	213.3	232.2	241.3	254.2	254.9	228.4	187.6	158.9	144.5
70°	169.4	173.2	178.5	187.6	193.6	196.7	195.2	171.7	141.5	124.1	111.2
72.5°	141.5	140.7	144.5	144.5	150.5	149.8	145.2	127.1	107.4	93.0	85.5
75°	111.2	112.0	112.7	111.2	108.9	105.9	102.1	88.5	75.6	68.8	62.0
77.5°	87.0	85.5	86.2	80.9	77.9	74.9	69.6	62.8	52.2	50.7	47.7
80°	62.0	61.3	60.5	58.2	51.4	48.4	44.6	40.8	38.6	37.1	36.3
82.5°	41.6	41.6	40.1	35.6	31.8	29.5	28.7	27.2	25.0	25.0	24.2
85°	25.0	24.2	22.7	18.2	15.9	15.9	15.9	15.9	14.4	14.4	13.6
87.5°	9.8	9.1	6.8	6.8	6.1	6.1	6.1	5.3	5.3	4.5	4.5
90°	1.1	2.3	3.4	5.1	6.2	6.8	7.4	9.1	10.8	12.5	14.2
92.5°	8.5	12.5	18.1	23.2	28.9	34.0	39.1	57.2	87.3	116.7	105.4
95°	19.3	21.0	27.2	36.8	51.6	62.6	73.7	121.8	206.2	299.2	336.0
97.5°	30.6	31.2	36.3	44.8	59.5	71.7	83.9	131.5	229.5	385.9	516.7
100°	41.9	42.5	46.5	54.4	68.0	79.0	90.1	129.8	213.6	362.6	536.6
102.5°	53.8	55.0	58.4	65.7	77.6	87.6	97.5	132.0	200.0	328.6	499.7
105°	65.7	67.4	70.8	77.6	88.4	97.2	106.0	136.6	194.9	302.0	455.5
107.5°	78.2	79.9	83.3	90.1	100.3	108.5	116.7	143.9	193.8	282.7	416.5
110°	91.8	93.5	96.3	102.6	112.2	120.2	128.1	153.5	196.6	272.5	384.2

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	104.3	106.0	108.8	115.0	124.7	132.4	140.0	163.2	202.3	266.9	362.6
115°	116.2	118.4	121.8	127.5	137.1	144.8	152.4	173.9	208.5	266.3	348.5
117.5°	128.1	130.9	133.7	138.8	149.6	156.6	163.7	185.3	216.4	266.9	338.8
120°	140.5	142.2	145.1	150.7	161.5	168.6	175.6	196.0	225.5	269.1	332.6
122.5°	151.3	153.0	155.8	162.0	172.2	179.8	187.5	207.4	234.0	273.1	328.6
125°	161.5	162.6	166.0	172.2	183.0	190.6	198.3	218.1	243.1	277.1	325.2
127.5°	169.4	171.1	175.1	181.3	193.2	200.8	208.5	227.8	250.4	281.6	323.5
130°	176.8	178.5	183.6	190.4	202.3	210.0	217.6	236.3	257.8	286.1	321.8
132.5°	182.4	184.7	190.4	198.9	210.8	218.2	225.5	243.6	264.6	289.5	321.3
135°	189.2	191.5	197.7	206.2	218.1	225.8	233.4	251.0	270.3	292.9	320.7
137.5°	195.5	197.7	204.0	213.0	224.9	232.0	239.1	256.1	274.8	295.2	319.6
140°	201.7	204.5	210.2	219.3	230.6	237.7	244.8	261.2	278.2	297.5	319.0
142.5°	208.5	210.8	217.0	224.9	236.3	242.8	249.3	265.2	281.6	299.2	317.9
145°	215.9	217.6	222.7	231.2	240.8	247.3	253.8	268.6	283.9	299.7	316.7
147.5°	223.2	224.4	229.5	236.8	246.5	252.2	257.8	271.4	285.6	299.7	315.0
150°	230.6	231.2	235.7	243.1	251.0	256.1	261.2	274.2	286.1	299.7	312.8
152.5°	238.0	238.0	242.5	248.7	255.5	260.4	265.2	275.9	287.3	298.0	309.9
155°	245.3	245.3	248.7	254.4	260.6	264.6	268.6	278.2	287.3	296.9	306.5
157.5°	251.0	251.6	254.4	259.5	265.2	268.3	271.4	279.3	287.8	295.2	303.7
160°	257.8	257.8	260.1	264.6	268.6	271.4	274.2	281.0	287.8	294.1	300.3
162.5°	262.9	262.9	264.6	268.0	271.4	273.6	275.9	281.6	287.3	291.8	296.9
165°	268.0	267.4	268.6	271.4	273.7	275.6	277.6	282.2	286.1	289.5	293.5
167.5°	272.0	271.4	272.0	274.2	275.9	277.4	278.8	282.2	285.6	287.3	290.1
170°	275.4	274.2	274.8	276.5	277.6	278.2	278.8	281.6	283.9	285.0	286.7
172.5°	277.6	277.1	277.1	278.2	278.8	279.0	279.3	281.6	283.3	283.3	283.9
175°	279.3	278.8	278.2	279.3	279.3	279.6	279.9	281.0	282.2	281.6	281.6
177.5°	280.5	279.9	279.3	279.9	279.9	279.9	279.9	280.5	281.6	280.5	279.9
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	932.7	932.7	939.5	946.3	942.5	944.8	953.1	950.1	956.1	955.4	957.6
5°	1003.0	1011.4	1018.2	1032.5	1034.8	1032.5	1046.9	1050.7	1057.5	1049.2	1053.0
7.5°	1082.5	1099.9	1116.5	1137.7	1144.5	1146.0	1153.6	1164.2	1173.2	1156.6	1164.9
10°	1159.6	1186.1	1220.1	1239.0	1255.7	1261.7	1267.8	1274.6	1285.2	1295.0	1287.5
12.5°	1242.8	1281.4	1313.9	1348.0	1368.4	1366.1	1383.5	1388.1	1396.4	1398.6	1401.7
15°	1310.9	1365.4	1385.8	1436.5	1441.0	1456.1	1475.8	1493.2	1495.5	1490.9	1490.9
17.5°	1376.0	1422.9	1459.2	1500.0	1508.3	1521.2	1546.2	1554.5	1557.5	1556.7	1556.7
20°	1428.9	1459.9	1521.2	1555.2	1568.8	1585.5	1602.9	1613.5	1615.7	1618.8	1614.2
22.5°	1463.7	1510.6	1560.5	1588.5	1599.9	1605.9	1617.3	1620.3	1616.5	1617.3	1618.0
25°	1490.9	1537.1	1567.3	1574.9	1574.1	1566.6	1558.3	1543.9	1542.4	1536.3	1524.2
27.5°	1498.5	1515.9	1512.1	1481.1	1450.1	1447.1	1397.1	1369.9	1338.9	1343.4	1326.0
30°	1457.6	1435.0	1381.2	1302.6	1270.1	1217.1	1161.1	1102.9	1080.2	1055.2	1101.4
32.5°	1357.8	1276.9	1181.5	1079.4	1025.0	978.1	918.3	876.0	851.7	831.3	870.7
35°	1207.3	1080.9	954.6	857.8	813.2	770.8	714.8	693.6	663.4	666.4	670.2
37.5°	1013.6	874.4	779.1	683.8	654.3	636.9	596.1	563.5	553.0	549.9	549.9
40°	832.1	717.9	633.1	558.2	535.6	521.2	488.7	473.5	462.2	459.2	462.9
42.5°	688.4	590.8	525.0	475.0	459.2	441.0	427.4	408.5	406.2	400.9	407.7
45°	577.9	493.2	444.0	407.7	394.1	387.3	372.2	360.8	356.3	355.5	360.8
47.5°	490.2	424.4	381.2	358.5	348.0	341.2	328.3	323.8	319.2	320.7	318.5
50°	411.5	362.3	334.3	313.9	307.1	300.3	292.0	287.4	285.2	285.2	284.4
52.5°	353.3	312.4	294.3	275.3	272.3	268.5	259.5	256.4	252.6	251.9	254.9
55°	302.6	274.6	256.4	245.1	242.1	234.5	230.7	226.9	224.7	223.1	223.9
57.5°	258.7	237.5	225.4	215.6	210.3	207.3	200.5	199.7	198.2	198.2	197.4
60°	222.4	207.3	192.9	186.8	183.1	179.3	178.5	174.0	171.7	173.2	172.5
62.5°	188.4	176.2	167.9	161.1	158.9	155.8	153.6	152.0	149.8	150.5	150.5
65°	157.3	147.5	141.5	135.4	134.6	131.6	130.9	129.4	129.4	128.6	130.1
67.5°	129.4	122.5	117.2	113.5	111.2	112.0	108.9	106.7	106.7	105.9	108.2
70°	102.9	99.1	93.8	89.3	86.2	86.2	82.5	81.7	81.7	81.7	80.9
72.5°	79.4	72.6	70.3	68.8	68.8	68.8	67.3	67.3	66.6	67.3	66.6
75°	59.0	58.2	56.7	56.0	56.0	55.2	54.5	54.5	54.5	54.5	54.5
77.5°	46.1	46.1	44.6	43.9	43.9	43.9	43.1	43.1	42.4	42.4	42.4
80°	34.0	34.0	32.5	32.5	32.5	31.8	31.8	31.8	32.5	31.8	31.8
82.5°	23.4	23.4	22.7	23.4	22.7	21.9	21.9	21.9	21.2	21.9	21.9
85°	13.6	13.6	12.9	12.1	12.9	12.9	12.1	12.9	12.1	12.9	12.1
87.5°	5.3	4.5	4.5	4.5	3.8	4.5	3.8	3.8	4.5	3.8	4.5
90°	13.6	14.2	14.7	15.3	15.8	16.4	15.9	16.4	17.0	16.4	17.0
92.5°	78.8	56.1	43.6	38.0	36.0	34.0	32.9	30.6	31.2	30.0	31.2
95°	272.5	204.0	138.3	108.2	98.0	87.8	77.1	72.0	68.0	65.7	68.0
97.5°	534.3	468.6	353.6	278.8	246.5	214.2	176.2	154.7	141.1	134.9	141.1
100°	648.2	668.0	622.1	555.8	515.6	475.4	418.2	376.8	354.7	355.3	354.7
102.5°	653.9	734.3	743.9	712.2	690.4	668.6	627.2	596.6	579.1	562.6	579.1
105°	618.2	736.6	793.2	804.0	796.6	789.3	763.2	741.7	723.6	720.7	723.6
107.5°	567.2	702.6	791.5	835.7	843.4	851.0	847.6	837.4	830.1	823.8	830.1
110°	519.6	649.3	753.6	825.0	844.8	864.6	880.5	885.0	883.9	882.8	883.9

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	478.2	596.6	703.7	785.9	812.8	839.7	872.0	888.4	894.1	894.7	894.1
115°	446.5	551.3	649.9	733.2	764.0	794.9	837.4	862.4	873.7	876.5	873.7
117.5°	425.5	516.2	603.4	679.9	711.9	743.9	788.1	815.9	832.9	836.9	832.9
120°	409.7	489.5	566.0	634.0	662.6	691.3	736.0	767.7	781.3	784.7	781.3
122.5°	396.6	468.6	536.0	597.8	623.8	649.9	688.4	716.2	731.5	736.0	731.5
125°	385.9	450.4	512.2	566.6	589.2	611.9	648.2	673.1	687.3	691.3	687.3
127.5°	375.7	434.0	490.1	540.0	561.0	581.9	614.8	636.3	649.3	652.7	649.3
130°	367.7	418.7	469.7	515.6	534.8	554.1	584.2	604.6	616.5	621.0	616.5
132.5°	360.4	404.6	450.4	492.4	510.5	528.6	556.4	576.8	587.0	589.8	587.0
135°	354.1	392.1	432.3	469.1	485.2	501.4	529.2	546.2	556.4	560.4	556.4
137.5°	348.5	380.2	414.2	447.0	461.4	475.9	499.7	517.3	525.8	529.2	525.8
140°	343.4	370.0	398.9	426.1	438.2	450.4	472.0	487.8	496.9	496.3	496.9
142.5°	338.8	360.4	384.2	406.8	417.0	427.2	444.8	458.4	466.3	465.7	466.3
145°	334.9	353.0	371.7	389.8	398.0	406.3	420.4	432.3	436.9	438.0	436.9
147.5°	330.9	346.8	362.1	377.4	383.4	389.3	400.6	409.1	413.6	414.2	413.6
150°	326.9	340.0	353.0	364.9	370.3	375.7	384.2	390.4	393.8	393.8	393.8
152.5°	322.4	333.7	344.5	354.7	359.0	363.2	369.4	375.1	376.8	376.8	376.8
155°	317.9	327.5	336.6	345.1	348.5	351.9	357.0	361.5	362.6	363.2	362.6
157.5°	312.8	320.7	328.6	335.4	338.2	341.1	345.6	349.0	350.2	350.2	350.2
160°	307.7	315.0	321.3	326.9	328.9	330.9	334.9	338.3	338.3	337.7	338.3
162.5°	302.6	308.2	313.3	318.4	320.1	321.8	324.1	326.9	326.9	326.4	326.9
165°	298.0	302.6	306.0	309.9	311.4	312.8	315.0	317.3	316.7	316.7	316.7
167.5°	293.5	297.5	300.3	302.6	303.7	304.8	306.0	307.7	307.1	307.1	307.1
170°	289.5	292.4	294.1	296.3	296.9	297.5	298.0	299.2	298.6	298.6	298.6
172.5°	285.6	287.8	289.0	290.7	291.0	291.2	291.2	292.4	291.2	290.7	291.2
175°	282.7	283.9	284.4	285.6	285.6	285.6	285.6	286.1	285.6	285.0	285.6
177.5°	280.5	281.0	281.6	282.2	282.2	282.2	281.6	282.2	281.0	281.0	281.0
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	953.9	949.3	946.3	944.0	941.8	948.6	939.5	929.7	922.8	918.3	916.8
5°	1053.7	1043.9	1035.6	1028.7	1030.3	1030.3	1014.4	997.0	981.9	973.5	964.5
7.5°	1169.4	1158.9	1142.2	1138.4	1135.4	1116.5	1100.6	1068.8	1049.9	1031.0	1014.4
10°	1284.4	1270.8	1254.9	1249.6	1242.1	1218.6	1194.4	1153.6	1130.1	1095.3	1073.4
12.5°	1391.8	1375.2	1359.3	1355.5	1344.2	1323.8	1282.2	1239.8	1199.7	1162.6	1124.1
15°	1481.9	1477.3	1453.1	1438.0	1413.0	1385.0	1376.0	1318.5	1267.8	1229.2	1159.6
17.5°	1557.5	1536.3	1513.6	1503.8	1494.0	1461.4	1428.9	1369.9	1315.4	1258.7	1214.1
20°	1618.0	1594.6	1578.7	1564.3	1559.8	1522.7	1471.3	1419.1	1359.3	1295.8	1237.5
22.5°	1621.0	1618.0	1607.4	1599.1	1590.0	1565.8	1525.0	1459.9	1396.4	1326.8	1250.4
25°	1558.3	1553.7	1584.0	1576.4	1582.5	1573.4	1551.4	1497.0	1422.9	1341.2	1264.0
27.5°	1369.1	1415.3	1462.9	1479.6	1490.9	1523.5	1534.0	1503.8	1444.0	1357.0	1270.8
30°	1112.0	1173.2	1250.4	1292.0	1323.8	1384.3	1462.9	1472.8	1444.8	1375.2	1269.3
32.5°	872.9	928.9	990.9	1040.1	1082.5	1206.5	1312.4	1388.8	1402.4	1366.1	1273.1
35°	703.5	727.7	786.7	833.6	891.1	997.0	1121.8	1245.1	1328.3	1332.8	1261.7
37.5°	580.2	593.0	644.5	671.0	705.0	798.0	914.5	1075.6	1205.0	1266.3	1230.0
40°	480.3	509.8	539.3	554.5	578.7	643.0	754.9	881.2	1041.6	1155.1	1180.8
42.5°	416.8	429.7	448.6	469.7	484.9	540.9	615.7	731.5	876.0	1034.0	1105.1
45°	367.6	372.2	391.8	405.4	421.3	460.7	513.6	610.4	737.5	893.3	1014.4
47.5°	326.8	335.9	346.4	354.8	365.4	395.6	441.0	511.3	623.3	762.5	892.6
50°	290.5	295.8	309.4	313.2	320.7	341.9	376.7	430.4	522.7	633.9	768.5
52.5°	256.4	266.3	271.6	276.9	283.7	301.1	323.8	367.6	437.2	541.6	655.8
55°	230.0	233.0	240.5	245.1	250.4	262.5	282.1	314.7	369.1	452.3	560.5
57.5°	204.2	204.2	211.8	215.6	220.9	230.0	247.4	272.3	311.7	373.7	472.8
60°	177.0	177.8	183.8	188.4	189.9	198.9	213.3	233.0	263.2	308.6	389.6
62.5°	152.8	156.6	159.6	161.1	166.4	171.7	183.8	197.4	218.6	258.7	316.2
65°	132.4	133.1	135.4	136.9	139.2	145.2	154.3	163.4	181.5	211.0	257.9
67.5°	108.9	112.0	115.0	115.0	117.2	120.3	129.4	136.9	150.5	167.9	199.7
70°	81.7	83.2	87.7	90.0	93.0	98.3	102.9	107.4	118.0	130.9	155.1
72.5°	68.1	68.1	69.6	70.3	70.3	74.1	80.9	85.5	90.8	99.8	116.5
75°	54.5	54.5	56.7	56.0	57.5	59.0	59.8	62.8	65.8	72.6	82.5
77.5°	43.1	43.9	43.9	44.6	44.6	45.4	46.1	47.7	49.2	53.0	57.5
80°	31.8	32.5	32.5	33.3	33.3	34.0	34.8	35.6	37.1	38.6	40.8
82.5°	21.9	22.7	22.7	23.4	22.7	23.4	24.2	24.2	25.0	26.5	27.2
85°	12.9	12.9	13.6	12.9	12.9	12.9	13.6	13.6	14.4	16.6	16.6
87.5°	3.8	4.5	3.8	4.5	4.5	4.5	4.5	5.3	5.3	6.1	6.8
90°	16.4	15.9	16.4	15.8	15.3	14.7	14.2	13.6	14.2	12.5	10.8
92.5°	30.6	32.9	34.0	36.0	38.0	43.6	56.1	78.8	105.4	116.7	87.3
95°	72.0	77.1	87.8	98.0	108.2	138.3	204.0	272.5	336.0	299.2	206.2
97.5°	154.7	176.2	214.2	246.5	278.8	353.6	468.6	534.3	516.7	385.9	229.5
100°	376.8	418.2	475.4	515.6	555.8	622.1	668.0	648.2	536.6	362.6	213.6
102.5°	596.6	627.2	668.6	690.4	712.2	743.9	734.3	653.9	499.7	328.6	200.0
105°	741.7	763.2	789.3	796.6	804.0	793.2	736.6	618.2	455.5	302.0	194.9
107.5°	837.4	847.6	851.0	843.4	835.7	791.5	702.6	567.2	416.5	282.7	193.8
110°	885.0	880.5	864.6	844.8	825.0	753.6	649.3	519.6	384.2	272.5	196.6

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	888.4	872.0	839.7	812.8	785.9	703.7	596.6	478.2	362.6	266.9	202.3
115°	862.4	837.4	794.9	764.0	733.2	649.9	551.3	446.5	348.5	266.3	208.5
117.5°	815.9	788.1	743.9	711.9	679.9	603.4	516.2	425.5	338.8	266.9	216.4
120°	767.7	736.0	691.3	662.6	634.0	566.0	489.5	409.7	332.6	269.1	225.5
122.5°	716.2	688.4	649.9	623.8	597.8	536.0	468.6	396.6	328.6	273.1	234.0
125°	673.1	648.2	611.9	589.2	566.6	512.2	450.4	385.9	325.2	277.1	243.1
127.5°	636.3	614.8	581.9	561.0	540.0	490.1	434.0	375.7	323.5	281.6	250.4
130°	604.6	584.2	554.1	534.8	515.6	469.7	418.7	367.7	321.8	286.1	257.8
132.5°	576.8	556.4	528.6	510.5	492.4	450.4	404.6	360.4	321.3	289.5	264.6
135°	546.2	529.2	501.4	485.2	469.1	432.3	392.1	354.1	320.7	292.9	270.3
137.5°	517.3	499.7	475.9	461.4	447.0	414.2	380.2	348.5	319.6	295.2	274.8
140°	487.8	472.0	450.4	438.2	426.1	398.9	370.0	343.4	319.0	297.5	278.2
142.5°	458.4	444.8	427.2	417.0	406.8	384.2	360.4	338.8	317.9	299.2	281.6
145°	432.3	420.4	406.3	398.0	389.8	371.7	353.0	334.9	316.7	299.7	283.9
147.5°	409.1	400.6	389.3	383.4	377.4	362.1	346.8	330.9	315.0	299.7	285.6
150°	390.4	384.2	375.7	370.3	364.9	353.0	340.0	326.9	312.8	299.7	286.1
152.5°	375.1	369.4	363.2	359.0	354.7	344.5	333.7	322.4	309.9	298.0	287.3
155°	361.5	357.0	351.9	348.5	345.1	336.6	327.5	317.9	306.5	296.9	287.3
157.5°	349.0	345.6	341.1	338.2	335.4	328.6	320.7	312.8	303.7	295.2	287.8
160°	338.3	334.9	330.9	328.9	326.9	321.3	315.0	307.7	300.3	294.1	287.8
162.5°	326.9	324.1	321.8	320.1	318.4	313.3	308.2	302.6	296.9	291.8	287.3
165°	317.3	315.0	312.8	311.4	309.9	306.0	302.6	298.0	293.5	289.5	286.1
167.5°	307.7	306.0	304.8	303.7	302.6	300.3	297.5	293.5	290.1	287.3	285.6
170°	299.2	298.0	297.5	296.9	296.3	294.1	292.4	289.5	286.7	285.0	283.9
172.5°	292.4	291.2	291.2	291.0	290.7	289.0	287.8	285.6	283.9	283.3	283.3
175°	286.1	285.6	285.6	285.6	285.6	284.4	283.9	282.7	281.6	281.6	282.2
177.5°	282.2	281.6	282.2	282.2	282.2	281.6	281.0	280.5	279.9	280.5	281.6
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	914.5	910.7	907.0	907.0	898.6	891.1	887.3	888.8	884.3	878.2	872.2
5°	954.6	939.5	936.5	928.1	916.8	900.9	892.6	885.0	876.0	863.8	852.5
7.5°	991.7	972.0	961.4	953.1	931.2	909.2	891.1	879.0	863.1	844.9	831.3
10°	1040.1	1003.8	992.4	973.5	942.5	911.5	890.3	870.7	848.7	827.5	809.4
12.5°	1078.7	1037.1	1015.9	997.0	956.9	917.6	882.0	857.8	831.3	807.9	784.4
15°	1122.5	1075.6	1038.6	1015.9	965.2	917.6	877.5	843.4	813.9	785.2	764.8
17.5°	1143.7	1084.7	1068.1	1035.6	962.2	914.5	865.4	829.1	793.5	760.2	736.0
20°	1177.0	1108.2	1066.6	1044.6	979.6	909.2	851.7	810.1	773.1	737.5	711.8
22.5°	1179.3	1104.4	1077.2	1035.6	955.4	893.3	839.6	789.0	745.8	712.6	686.1
25°	1174.0	1097.6	1059.8	1026.5	959.9	884.3	815.4	765.5	723.2	684.6	653.6
27.5°	1171.7	1077.9	1042.4	1009.1	934.2	857.8	801.1	744.3	695.9	661.9	630.1
30°	1168.7	1056.7	1013.6	975.0	906.2	837.4	769.3	720.1	674.0	630.9	599.1
32.5°	1149.0	1028.0	984.1	943.3	869.1	800.3	746.6	694.4	644.5	604.4	575.6
35°	1143.0	1001.5	944.0	900.2	827.5	766.3	709.5	666.4	619.5	579.4	545.4
37.5°	1125.6	974.3	912.3	856.3	780.6	722.4	680.8	637.7	592.3	549.2	521.9
40°	1095.3	942.5	872.2	814.7	736.8	677.8	639.2	607.4	562.8	524.2	490.9
42.5°	1050.7	910.0	834.3	773.8	687.6	632.4	600.6	570.4	532.5	492.4	465.2
45°	999.2	866.9	796.5	729.2	641.5	587.7	554.5	536.3	501.5	467.5	435.7
47.5°	928.9	822.2	752.7	683.1	593.8	541.6	515.1	497.0	472.8	435.7	410.0
50°	840.4	764.8	698.9	636.9	546.9	497.0	470.5	456.9	436.5	410.0	385.0
52.5°	742.1	698.2	643.7	586.2	499.2	452.3	428.1	417.6	402.4	377.5	356.3
55°	643.0	624.1	587.0	530.3	449.3	410.7	389.6	375.9	364.6	346.4	328.3
57.5°	554.5	545.4	519.7	475.8	407.7	367.6	349.5	340.4	331.3	317.7	299.5
60°	462.9	472.8	446.3	424.4	362.3	327.5	311.7	301.8	297.3	285.2	273.8
62.5°	383.5	392.6	377.5	360.8	316.9	285.9	276.1	267.0	264.0	253.4	242.1
65°	311.7	323.0	311.7	302.6	276.1	250.4	238.3	233.7	230.7	223.9	214.8
67.5°	248.1	259.5	254.2	242.8	234.5	213.3	206.5	202.0	200.5	195.2	187.6
70°	186.8	202.7	204.2	197.4	189.9	180.0	175.5	174.0	170.2	165.7	161.1
72.5°	134.6	152.8	153.6	153.6	149.0	149.0	144.5	142.2	142.2	137.7	132.4
75°	99.1	111.2	112.7	114.2	116.5	118.8	115.7	115.7	115.0	110.4	108.2
77.5°	65.8	76.4	80.2	85.5	88.5	88.5	90.0	91.5	90.0	87.7	86.2
80°	42.4	49.9	54.5	57.5	62.0	64.3	66.6	67.3	65.8	65.1	62.8
82.5°	28.0	30.3	32.5	36.3	41.6	45.4	45.4	44.6	46.1	45.4	44.6
85°	15.9	17.4	18.2	18.9	21.9	25.7	26.5	27.2	28.7	27.2	25.7
87.5°	6.1	6.8	6.8	6.8	8.3	9.1	11.3	14.4	13.6	12.1	12.1
90°	9.1	7.4	6.8	6.2	5.1	3.4	2.3	1.1	2.3	3.4	5.1
92.5°	57.2	39.1	34.0	28.9	23.2	18.1	12.5	8.5	12.5	18.1	23.2
95°	121.8	73.7	62.6	51.6	36.8	27.2	21.0	19.3	21.0	27.2	36.8
97.5°	131.5	83.9	71.7	59.5	44.8	36.3	31.2	30.6	31.2	36.3	44.8
100°	129.8	90.1	79.0	68.0	54.4	46.5	42.5	41.9	42.5	46.5	54.4
102.5°	132.0	97.5	87.6	77.6	65.7	58.4	55.0	53.8	55.0	58.4	65.7
105°	136.6	106.0	97.2	88.4	77.6	70.8	67.4	65.7	67.4	70.8	77.6
107.5°	143.9	116.7	108.5	100.3	90.1	83.3	79.9	78.2	79.9	83.3	90.1
110°	153.5	128.1	120.2	112.2	102.6	96.3	93.5	91.8	93.5	96.3	102.6

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	163.2	140.0	132.4	124.7	115.0	108.8	106.0	104.3	106.0	108.8	115.0
115°	173.9	152.4	144.8	137.1	127.5	121.8	118.4	116.2	118.4	121.8	127.5
117.5°	185.3	163.7	156.6	149.6	138.8	133.7	130.9	128.1	130.9	133.7	138.8
120°	196.0	175.6	168.6	161.5	150.7	145.1	142.2	140.5	142.2	145.1	150.7
122.5°	207.4	187.5	179.8	172.2	162.0	155.8	153.0	151.3	153.0	155.8	162.0
125°	218.1	198.3	190.6	183.0	172.2	166.0	162.6	161.5	162.6	166.0	172.2
127.5°	227.8	208.5	200.8	193.2	181.3	175.1	171.1	169.4	171.1	175.1	181.3
130°	236.3	217.6	210.0	202.3	190.4	183.6	178.5	176.8	178.5	183.6	190.4
132.5°	243.6	225.5	218.2	210.8	198.9	190.4	184.7	182.4	184.7	190.4	198.9
135°	251.0	233.4	225.8	218.1	206.2	197.7	191.5	189.2	191.5	197.7	206.2
137.5°	256.1	239.1	232.0	224.9	213.0	204.0	197.7	195.5	197.7	204.0	213.0
140°	261.2	244.8	237.7	230.6	219.3	210.2	204.5	201.7	204.5	210.2	219.3
142.5°	265.2	249.3	242.8	236.3	224.9	217.0	210.8	208.5	210.8	217.0	224.9
145°	268.6	253.8	247.3	240.8	231.2	222.7	217.6	215.9	217.6	222.7	231.2
147.5°	271.4	257.8	252.2	246.5	236.8	229.5	224.4	223.2	224.4	229.5	236.8
150°	274.2	261.2	256.1	251.0	243.1	235.7	231.2	230.6	231.2	235.7	243.1
152.5°	275.9	265.2	260.4	255.5	248.7	242.5	238.0	238.0	238.0	242.5	248.7
155°	278.2	268.6	264.6	260.6	254.4	248.7	245.3	245.3	245.3	248.7	254.4
157.5°	279.3	271.4	268.3	265.2	259.5	254.4	251.6	251.0	251.6	254.4	259.5
160°	281.0	274.2	271.4	268.6	264.6	260.1	257.8	257.8	257.8	260.1	264.6
162.5°	281.6	275.9	273.6	271.4	268.0	264.6	262.9	262.9	262.9	264.6	268.0
165°	282.2	277.6	275.6	273.7	271.4	268.6	267.4	268.0	267.4	268.6	271.4
167.5°	282.2	278.8	277.4	275.9	274.2	272.0	271.4	272.0	271.4	272.0	274.2
170°	281.6	278.8	278.2	277.6	276.5	274.8	274.2	275.4	274.2	274.8	276.5
172.5°	281.6	279.3	279.0	278.8	278.2	277.1	277.1	277.6	277.1	277.1	278.2
175°	281.0	279.9	279.6	279.3	279.3	278.2	278.8	279.3	278.8	278.2	279.3
177.5°	280.5	279.9	279.9	279.9	279.9	279.3	279.9	280.5	279.9	279.3	279.9
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	872.2	868.4	866.9	863.1	854.0	848.0	841.2	836.6	837.4	833.6	835.9
5°	844.9	844.2	838.9	831.3	818.5	811.7	799.6	793.5	790.5	791.2	786.7
7.5°	822.2	815.4	811.7	799.6	787.4	773.1	763.2	757.9	753.4	748.9	745.8
10°	796.5	790.5	784.4	771.6	754.9	741.3	727.7	722.4	715.6	712.6	710.3
12.5°	769.3	765.5	757.9	742.8	723.9	711.0	695.2	692.1	683.1	677.0	675.5
15°	744.3	742.1	728.4	711.0	692.1	679.3	665.7	656.6	641.5	644.5	639.2
17.5°	717.9	708.0	699.7	676.3	667.2	647.5	631.6	627.1	616.5	609.7	602.9
20°	688.4	682.3	671.7	656.6	634.6	612.0	599.9	592.3	586.2	575.6	572.6
22.5°	660.4	652.8	643.7	624.1	605.1	586.2	569.6	562.8	555.2	547.7	543.1
25°	638.4	627.1	617.2	593.0	574.1	558.2	547.7	536.3	525.7	521.2	519.7
27.5°	604.4	597.6	587.7	565.1	547.7	530.3	520.4	512.9	501.5	496.2	491.7
30°	582.5	568.8	557.5	539.3	521.9	503.0	494.0	484.9	478.1	471.3	466.0
32.5°	553.0	542.4	533.3	515.1	497.7	480.3	470.5	456.9	453.1	447.8	441.8
35°	524.2	517.4	507.6	487.9	469.0	456.9	446.3	433.4	428.9	425.1	419.8
37.5°	497.0	487.1	480.3	461.4	444.8	430.4	422.1	411.5	408.5	403.9	400.2
40°	473.5	463.7	456.9	438.0	420.6	405.4	400.2	389.6	385.0	379.7	377.5
42.5°	447.1	438.7	429.7	416.0	397.9	382.8	372.2	366.1	360.1	357.8	353.3
45°	419.1	411.5	404.7	389.6	370.7	360.1	351.0	342.7	338.1	334.3	331.3
47.5°	394.9	388.1	379.0	362.3	347.2	337.4	328.3	320.0	315.4	310.9	307.1
50°	366.9	363.1	353.3	337.4	323.0	311.7	303.3	295.8	292.7	287.4	281.4
52.5°	341.9	335.1	326.8	313.9	301.1	287.4	276.1	271.6	266.3	263.2	257.9
55°	312.4	307.9	298.8	287.4	273.8	262.5	254.2	248.1	241.3	238.3	231.5
57.5°	287.4	279.1	274.6	260.2	247.4	236.0	230.0	223.9	216.3	211.8	208.8
60°	260.2	252.6	245.8	233.7	224.7	212.6	203.5	198.2	192.9	186.8	183.8
62.5°	233.7	227.7	219.4	209.5	198.2	188.4	181.5	174.0	171.0	164.9	162.6
65°	205.0	200.5	193.6	182.3	173.2	164.9	158.1	152.0	149.0	146.7	145.2
67.5°	179.3	173.2	168.7	158.9	149.0	142.2	138.4	134.6	130.9	128.6	126.3
70°	152.8	148.3	143.7	134.6	127.8	121.8	118.8	115.7	113.5	111.2	108.9
72.5°	125.6	123.3	118.8	112.7	107.4	102.9	100.6	96.8	94.6	90.8	89.3
75°	103.6	99.8	97.6	92.3	87.7	84.0	80.9	76.4	73.4	71.9	71.1
77.5°	81.7	80.2	77.2	72.6	70.3	66.6	62.0	60.5	59.0	59.0	58.2
80°	61.3	59.0	56.7	53.0	50.7	47.7	47.7	47.7	46.9	47.7	46.9
82.5°	41.6	40.1	38.6	36.3	35.6	35.6	36.3	36.3	36.3	36.3	36.3
85°	24.2	24.2	24.2	25.0	24.2	24.2	25.0	25.7	25.0	25.0	24.2
87.5°	11.3	11.3	12.1	12.1	12.9	12.9	12.9	12.9	12.9	12.9	13.6
90°	6.2	6.8	7.4	9.1	10.8	12.5	14.2	13.6	14.2	14.7	15.3
92.5°	28.9	34.0	39.1	57.2	87.3	116.7	105.4	78.8	56.1	43.6	38.0
95°	51.6	62.6	73.7	121.8	206.2	299.2	336.0	272.5	204.0	138.3	108.2
97.5°	59.5	71.7	83.9	131.5	229.5	385.9	516.7	534.3	468.6	353.6	278.8
100°	68.0	79.0	90.1	129.8	213.6	362.6	536.6	648.2	668.0	622.1	555.8
102.5°	77.6	87.6	97.5	132.0	200.0	328.6	499.7	653.9	734.3	743.9	712.2
105°	88.4	97.2	106.0	136.6	194.9	302.0	455.5	618.2	736.6	793.2	804.0
107.5°	100.3	108.5	116.7	143.9	193.8	282.7	416.5	567.2	702.6	791.5	835.7
110°	112.2	120.2	128.1	153.5	196.6	272.5	384.2	519.6	649.3	753.6	825.0

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	124.7	132.4	140.0	163.2	202.3	266.9	362.6	478.2	596.6	703.7	785.9
115°	137.1	144.8	152.4	173.9	208.5	266.3	348.5	446.5	551.3	649.9	733.2
117.5°	149.6	156.6	163.7	185.3	216.4	266.9	338.8	425.5	516.2	603.4	679.9
120°	161.5	168.6	175.6	196.0	225.5	269.1	332.6	409.7	489.5	566.0	634.0
122.5°	172.2	179.8	187.5	207.4	234.0	273.1	328.6	396.6	468.6	536.0	597.8
125°	183.0	190.6	198.3	218.1	243.1	277.1	325.2	385.9	450.4	512.2	566.6
127.5°	193.2	200.8	208.5	227.8	250.4	281.6	323.5	375.7	434.0	490.1	540.0
130°	202.3	210.0	217.6	236.3	257.8	286.1	321.8	367.7	418.7	469.7	515.6
132.5°	210.8	218.2	225.5	243.6	264.6	289.5	321.3	360.4	404.6	450.4	492.4
135°	218.1	225.8	233.4	251.0	270.3	292.9	320.7	354.1	392.1	432.3	469.1
137.5°	224.9	232.0	239.1	256.1	274.8	295.2	319.6	348.5	380.2	414.2	447.0
140°	230.6	237.7	244.8	261.2	278.2	297.5	319.0	343.4	370.0	398.9	426.1
142.5°	236.3	242.8	249.3	265.2	281.6	299.2	317.9	338.8	360.4	384.2	406.8
145°	240.8	247.3	253.8	268.6	283.9	299.7	316.7	334.9	353.0	371.7	389.8
147.5°	246.5	252.2	257.8	271.4	285.6	299.7	315.0	330.9	346.8	362.1	377.4
150°	251.0	256.1	261.2	274.2	286.1	299.7	312.8	326.9	340.0	353.0	364.9
152.5°	255.5	260.4	265.2	275.9	287.3	298.0	309.9	322.4	333.7	344.5	354.7
155°	260.6	264.6	268.6	278.2	287.3	296.9	306.5	317.9	327.5	336.6	345.1
157.5°	265.2	268.3	271.4	279.3	287.8	295.2	303.7	312.8	320.7	328.6	335.4
160°	268.6	271.4	274.2	281.0	287.8	294.1	300.3	307.7	315.0	321.3	326.9
162.5°	271.4	273.6	275.9	281.6	287.3	291.8	296.9	302.6	308.2	313.3	318.4
165°	273.7	275.6	277.6	282.2	286.1	289.5	293.5	298.0	302.6	306.0	309.9
167.5°	275.9	277.4	278.8	282.2	285.6	287.3	290.1	293.5	297.5	300.3	302.6
170°	277.6	278.2	278.8	281.6	283.9	285.0	286.7	289.5	292.4	294.1	296.3
172.5°	278.8	279.0	279.3	281.6	283.3	283.3	283.9	285.6	287.8	289.0	290.7
175°	279.3	279.6	279.9	281.0	282.2	281.6	281.6	282.7	283.9	284.4	285.6
177.5°	279.9	279.9	279.9	280.5	281.6	280.5	279.9	280.5	281.0	281.6	282.2
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.1	835.9	833.6	829.1	828.3	829.8	834.3	832.8	829.1	835.9	829.8
5°	789.0	785.2	783.7	785.2	780.6	778.4	782.9	780.6	782.9	783.7	785.9
7.5°	744.3	745.1	740.5	741.3	735.3	736.8	736.8	736.8	739.0	740.5	743.6
10°	705.8	707.3	702.0	702.7	698.2	695.2	697.4	702.0	702.0	702.0	703.5
12.5°	674.7	667.9	664.1	663.4	658.1	656.6	661.1	662.6	666.4	666.4	668.7
15°	636.2	634.6	631.6	631.6	618.8	621.8	623.3	628.6	636.2	630.1	631.6
17.5°	601.4	597.6	593.8	592.3	590.8	586.2	592.3	591.5	596.1	596.8	599.1
20°	570.4	567.3	559.8	560.5	562.0	555.2	559.0	559.0	563.5	568.1	573.4
22.5°	540.1	537.1	533.3	534.8	530.3	528.7	528.7	532.5	537.8	541.6	540.9
25°	516.6	511.3	509.1	506.8	504.5	506.1	503.8	507.6	511.3	513.6	511.3
27.5°	490.2	487.9	483.4	481.1	477.3	478.8	480.3	483.4	485.6	485.6	487.9
30°	464.5	461.4	459.9	457.6	457.6	454.6	455.4	458.4	460.7	462.9	466.0
32.5°	439.5	437.2	434.9	434.9	433.4	432.7	431.9	436.5	436.5	441.0	441.0
35°	419.1	415.3	415.3	411.5	413.0	412.3	410.7	413.8	414.5	417.6	416.8
37.5°	396.4	396.4	394.9	391.1	388.1	388.8	392.6	392.6	394.9	394.1	396.4
40°	373.7	372.2	372.2	369.9	369.1	368.4	369.1	369.9	373.7	372.9	373.7
42.5°	351.0	351.7	348.0	348.0	348.0	345.7	346.4	347.2	348.7	350.2	352.5
45°	329.0	327.5	326.8	325.3	323.8	324.5	323.8	326.8	326.0	327.5	329.8
47.5°	305.6	303.3	302.6	299.5	299.5	301.1	300.3	302.6	303.3	305.6	304.1
50°	282.9	279.9	277.6	278.4	273.8	275.3	275.3	277.6	279.9	280.6	282.1
52.5°	256.4	255.7	254.9	251.1	250.4	249.6	250.4	251.1	254.2	256.4	257.2
55°	230.7	230.0	225.4	223.9	221.6	221.6	223.1	223.9	229.2	230.0	233.0
57.5°	207.3	205.0	199.7	198.9	198.9	198.9	196.7	199.7	201.2	205.0	205.0
60°	181.5	181.5	177.0	177.0	177.8	177.0	177.0	177.8	177.8	180.8	182.3
62.5°	161.1	160.4	160.4	158.9	158.1	158.9	158.1	158.1	158.9	161.1	163.4
65°	143.0	142.2	141.5	140.7	139.2	139.2	139.9	141.5	141.5	143.0	143.7
67.5°	125.6	125.6	124.1	124.1	123.3	122.5	123.3	122.5	125.6	125.6	126.3
70°	108.2	107.4	105.1	104.4	102.1	102.9	102.9	105.1	105.9	107.4	108.9
72.5°	87.0	87.0	85.5	84.0	84.7	83.2	83.2	84.0	84.0	86.2	87.0
75°	71.9	70.3	69.6	70.3	69.6	71.1	69.6	69.6	71.1	71.1	71.1
77.5°	59.0	59.0	58.2	58.2	59.0	58.2	59.0	59.0	59.0	58.2	59.0
80°	48.4	47.7	47.7	47.7	46.9	46.9	46.9	46.9	46.9	46.9	46.9
82.5°	36.3	36.3	35.6	36.3	36.3	35.6	36.3	35.6	35.6	36.3	36.3
85°	24.2	25.7	24.2	24.2	25.0	25.0	25.7	25.0	25.7	24.2	25.0
87.5°	12.9	13.6	13.6	12.9	12.9	13.6	13.6	13.6	14.4	12.9	13.6
90°	15.8	16.4	15.9	16.4	17.0	16.4	17.0	16.4	15.9	16.4	15.8
92.5°	36.0	34.0	32.9	30.6	31.2	30.0	31.2	30.6	32.9	34.0	36.0
95°	98.0	87.8	77.1	72.0	68.0	65.7	68.0	72.0	77.1	87.8	98.0
97.5°	246.5	214.2	176.2	154.7	141.1	134.9	141.1	154.7	176.2	214.2	246.5
100°	515.6	475.4	418.2	376.8	354.7	355.3	354.7	376.8	418.2	475.4	515.6
102.5°	690.4	668.6	627.2	596.6	579.1	562.6	579.1	596.6	627.2	668.6	690.4
105°	796.6	789.3	763.2	741.7	723.6	720.7	723.6	741.7	763.2	789.3	796.6
107.5°	843.4	851.0	847.6	837.4	830.1	823.8	830.1	837.4	847.6	851.0	843.4
110°	844.8	864.6	880.5	885.0	883.9	882.8	883.9	885.0	880.5	864.6	844.8

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	812.8	839.7	872.0	888.4	894.1	894.7	894.1	888.4	872.0	839.7	812.8
115°	764.0	794.9	837.4	862.4	873.7	876.5	873.7	862.4	837.4	794.9	764.0
117.5°	711.9	743.9	788.1	815.9	832.9	836.9	832.9	815.9	788.1	743.9	711.9
120°	662.6	691.3	736.0	767.7	781.3	784.7	781.3	767.7	736.0	691.3	662.6
122.5°	623.8	649.9	688.4	716.2	731.5	736.0	731.5	716.2	688.4	649.9	623.8
125°	589.2	611.9	648.2	673.1	687.3	691.3	687.3	673.1	648.2	611.9	589.2
127.5°	561.0	581.9	614.8	636.3	649.3	652.7	649.3	636.3	614.8	581.9	561.0
130°	534.8	554.1	584.2	604.6	616.5	621.0	616.5	604.6	584.2	554.1	534.8
132.5°	510.5	528.6	556.4	576.8	587.0	589.8	587.0	576.8	556.4	528.6	510.5
135°	485.2	501.4	529.2	546.2	556.4	560.4	556.4	546.2	529.2	501.4	485.2
137.5°	461.4	475.9	499.7	517.3	525.8	529.2	525.8	517.3	499.7	475.9	461.4
140°	438.2	450.4	472.0	487.8	496.9	496.3	496.9	487.8	472.0	450.4	438.2
142.5°	417.0	427.2	444.8	458.4	466.3	465.7	466.3	458.4	444.8	427.2	417.0
145°	398.0	406.3	420.4	432.3	436.9	438.0	436.9	432.3	420.4	406.3	398.0
147.5°	383.4	389.3	400.6	409.1	413.6	414.2	413.6	409.1	400.6	389.3	383.4
150°	370.3	375.7	384.2	390.4	393.8	393.8	393.8	390.4	384.2	375.7	370.3
152.5°	359.0	363.2	369.4	375.1	376.8	376.8	376.8	375.1	369.4	363.2	359.0
155°	348.5	351.9	357.0	361.5	362.6	363.2	362.6	361.5	357.0	351.9	348.5
157.5°	338.2	341.1	345.6	349.0	350.2	350.2	350.2	349.0	345.6	341.1	338.2
160°	328.9	330.9	334.9	338.3	338.3	337.7	338.3	338.3	334.9	330.9	328.9
162.5°	320.1	321.8	324.1	326.9	326.9	326.4	326.9	326.9	324.1	321.8	320.1
165°	311.4	312.8	315.0	317.3	316.7	316.7	316.7	317.3	315.0	312.8	311.4
167.5°	303.7	304.8	306.0	307.7	307.1	307.1	307.1	307.7	306.0	304.8	303.7
170°	296.9	297.5	298.0	299.2	298.6	298.6	298.6	299.2	298.0	297.5	296.9
172.5°	291.0	291.2	291.2	292.4	291.2	290.7	291.2	292.4	291.2	291.2	291.0
175°	285.6	285.6	285.6	286.1	285.6	285.0	285.6	286.1	285.6	285.6	285.6
177.5°	282.2	282.2	281.6	282.2	281.0	281.0	281.0	282.2	281.6	282.2	282.2
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.9	838.9	835.9	829.8	835.9	839.6	843.4	849.5	852.5	852.5	857.0
5°	788.2	794.3	792.0	790.5	796.5	800.3	806.4	813.9	822.2	827.5	833.6
7.5°	745.8	749.6	753.4	753.4	759.5	767.8	776.9	785.9	796.5	804.1	808.6
10°	708.8	711.8	714.1	717.1	726.2	735.3	747.4	758.7	767.8	776.1	783.7
12.5°	673.2	677.8	683.1	685.3	692.1	703.5	714.8	728.4	742.8	751.1	758.7
15°	639.2	641.5	647.5	654.3	660.4	672.5	686.8	701.2	713.3	726.2	733.0
17.5°	604.4	605.1	621.0	617.2	636.9	648.3	655.8	669.4	689.1	699.7	710.3
20°	570.4	577.9	584.7	588.5	599.1	612.0	633.9	644.5	660.4	670.2	679.3
22.5°	543.9	555.2	555.2	564.3	569.6	581.7	597.6	618.0	635.4	642.2	655.1
25°	520.4	525.7	534.8	537.8	547.7	558.2	568.8	590.8	609.7	618.8	627.8
27.5°	490.2	497.0	509.1	509.1	521.9	533.3	546.1	560.5	579.4	592.3	602.1
30°	466.7	473.5	478.8	487.1	492.4	503.0	525.7	536.3	553.0	564.3	576.4
32.5°	444.8	450.1	454.6	463.7	469.7	481.8	494.0	512.9	527.2	537.8	550.7
35°	420.6	425.9	431.9	438.7	447.8	459.2	470.5	486.4	500.8	510.6	521.2
37.5°	397.9	401.7	410.7	415.3	422.8	433.4	447.8	464.5	477.3	484.9	495.5
40°	375.9	379.0	385.8	394.1	399.4	407.7	422.8	437.2	453.1	462.2	470.5
42.5°	352.5	356.3	362.3	370.7	379.0	388.1	396.4	413.0	427.4	434.9	444.0
45°	332.1	334.3	338.9	347.2	355.5	362.3	375.2	390.3	403.9	410.0	419.8
47.5°	307.9	310.1	316.9	320.7	329.8	338.9	351.7	366.9	379.0	385.0	394.1
50°	282.9	285.2	289.7	298.0	304.1	313.9	325.3	338.1	353.3	361.6	366.9
52.5°	258.7	263.2	267.0	273.8	281.4	291.2	301.8	313.9	326.8	335.1	341.2
55°	234.5	238.3	242.8	246.6	255.7	264.8	276.9	288.2	299.5	307.1	313.9
57.5°	207.3	212.6	217.1	224.7	231.5	239.0	252.6	261.7	275.3	280.6	286.7
60°	183.8	189.1	192.9	198.9	205.0	214.8	223.9	235.3	246.6	253.4	261.0
62.5°	164.1	166.4	168.7	174.7	180.8	189.9	198.9	210.3	222.4	226.2	232.2
65°	144.5	146.7	150.5	155.8	160.4	165.7	175.5	184.6	195.9	202.0	204.2
67.5°	127.8	130.1	130.9	134.6	138.4	144.5	149.8	158.9	169.4	173.2	177.8
70°	108.9	112.7	113.5	116.5	118.0	121.8	127.8	134.6	143.0	149.8	153.6
72.5°	87.0	92.3	93.8	98.3	100.6	104.4	108.9	114.2	119.5	122.5	125.6
75°	71.1	72.6	73.4	77.2	80.9	86.2	88.5	91.5	96.1	99.8	102.9
77.5°	59.0	59.8	60.5	60.5	61.3	64.3	68.8	72.6	75.6	77.2	79.4
80°	47.7	46.9	46.9	47.7	47.7	47.7	49.2	54.5	56.0	59.8	59.0
82.5°	37.1	35.6	36.3	35.6	35.6	35.6	35.6	36.3	36.3	38.6	40.1
85°	24.2	25.0	24.2	24.2	23.4	24.2	23.4	23.4	22.7	22.7	21.9
87.5°	12.9	13.6	12.9	12.9	12.1	12.9	12.1	12.1	11.3	11.3	9.8
90°	15.3	14.7	14.2	13.6	14.2	12.5	10.8	9.1	7.4	6.8	6.2
92.5°	38.0	43.6	56.1	78.8	105.4	116.7	87.3	57.2	39.1	34.0	28.9
95°	108.2	138.3	204.0	272.5	336.0	299.2	206.2	121.8	73.7	62.6	51.6
97.5°	278.8	353.6	468.6	534.3	516.7	385.9	229.5	131.5	83.9	71.7	59.5
100°	555.8	622.1	668.0	648.2	536.6	362.6	213.6	129.8	90.1	79.0	68.0
102.5°	712.2	743.9	734.3	653.9	499.7	328.6	200.0	132.0	97.5	87.6	77.6
105°	804.0	793.2	736.6	618.2	455.5	302.0	194.9	136.6	106.0	97.2	88.4
107.5°	835.7	791.5	702.6	567.2	416.5	282.7	193.8	143.9	116.7	108.5	100.3
110°	825.0	753.6	649.3	519.6	384.2	272.5	196.6	153.5	128.1	120.2	112.2



TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	785.9	703.7	596.6	478.2	362.6	266.9	202.3	163.2	140.0	132.4	124.7
115°	733.2	649.9	551.3	446.5	348.5	266.3	208.5	173.9	152.4	144.8	137.1
117.5°	679.9	603.4	516.2	425.5	338.8	266.9	216.4	185.3	163.7	156.6	149.6
120°	634.0	566.0	489.5	409.7	332.6	269.1	225.5	196.0	175.6	168.6	161.5
122.5°	597.8	536.0	468.6	396.6	328.6	273.1	234.0	207.4	187.5	179.8	172.2
125°	566.6	512.2	450.4	385.9	325.2	277.1	243.1	218.1	198.3	190.6	183.0
127.5°	540.0	490.1	434.0	375.7	323.5	281.6	250.4	227.8	208.5	200.8	193.2
130°	515.6	469.7	418.7	367.7	321.8	286.1	257.8	236.3	217.6	210.0	202.3
132.5°	492.4	450.4	404.6	360.4	321.3	289.5	264.6	243.6	225.5	218.2	210.8
135°	469.1	432.3	392.1	354.1	320.7	292.9	270.3	251.0	233.4	225.8	218.1
137.5°	447.0	414.2	380.2	348.5	319.6	295.2	274.8	256.1	239.1	232.0	224.9
140°	426.1	398.9	370.0	343.4	319.0	297.5	278.2	261.2	244.8	237.7	230.6
142.5°	406.8	384.2	360.4	338.8	317.9	299.2	281.6	265.2	249.3	242.8	236.3
145°	389.8	371.7	353.0	334.9	316.7	299.7	283.9	268.6	253.8	247.3	240.8
147.5°	377.4	362.1	346.8	330.9	315.0	299.7	285.6	271.4	257.8	252.2	246.5
150°	364.9	353.0	340.0	326.9	312.8	299.7	286.1	274.2	261.2	256.1	251.0
152.5°	354.7	344.5	333.7	322.4	309.9	298.0	287.3	275.9	265.2	260.4	255.5
155°	345.1	336.6	327.5	317.9	306.5	296.9	287.3	278.2	268.6	264.6	260.6
157.5°	335.4	328.6	320.7	312.8	303.7	295.2	287.8	279.3	271.4	268.3	265.2
160°	326.9	321.3	315.0	307.7	300.3	294.1	287.8	281.0	274.2	271.4	268.6
162.5°	318.4	313.3	308.2	302.6	296.9	291.8	287.3	281.6	275.9	273.6	271.4
165°	309.9	306.0	302.6	298.0	293.5	289.5	286.1	282.2	277.6	275.6	273.7
167.5°	302.6	300.3	297.5	293.5	290.1	287.3	285.6	282.2	278.8	277.4	275.9
170°	296.3	294.1	292.4	289.5	286.7	285.0	283.9	281.6	278.8	278.2	277.6
172.5°	290.7	289.0	287.8	285.6	283.9	283.3	283.3	281.6	279.3	279.0	278.8
175°	285.6	284.4	283.9	282.7	281.6	281.6	282.2	281.0	279.9	279.6	279.3
177.5°	282.2	281.6	281.0	280.5	279.9	280.5	281.6	280.5	279.9	279.9	279.9
180°	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9	279.9

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	883.5	883.5	883.5	883.5
2.5°	860.8	866.1	876.7	885.8
5°	842.7	851.0	866.9	882.8
7.5°	820.7	833.6	854.0	876.0
10°	799.6	816.2	841.2	866.9
12.5°	778.4	795.8	822.2	855.5
15°	753.4	771.6	803.3	843.4
17.5°	731.5	755.7	784.4	824.5
20°	708.0	726.2	763.2	805.6
22.5°	678.5	708.8	743.6	788.2
25°	655.1	681.5	716.3	767.0
27.5°	626.3	657.3	699.7	744.3
30°	602.9	628.6	667.9	721.6
32.5°	575.6	605.9	646.8	699.7
35°	551.4	577.2	615.7	669.4
37.5°	522.7	550.7	593.8	641.5
40°	497.7	525.0	565.8	610.4
42.5°	467.5	496.2	537.1	574.9
45°	443.3	469.7	502.3	537.1
47.5°	413.8	441.8	473.5	497.7
50°	387.3	413.0	438.0	458.4
52.5°	358.5	382.0	404.7	419.8
55°	332.1	350.2	368.4	379.0
57.5°	301.1	318.5	333.6	339.6
60°	273.8	288.2	298.0	304.8
62.5°	245.1	255.7	263.2	267.0
65°	217.1	224.7	228.4	232.2
67.5°	188.4	195.2	197.4	202.0
70°	158.1	165.7	167.2	169.4
72.5°	135.4	135.4	138.4	141.5
75°	108.2	109.7	111.2	111.2
77.5°	84.7	84.7	86.2	87.0
80°	62.0	62.8	62.8	62.0
82.5°	42.4	43.9	42.4	41.6
85°	23.4	26.5	25.0	25.0
87.5°	9.8	9.8	11.3	9.8
90°	5.1	3.4	2.3	1.1
92.5°	23.2	18.1	12.5	8.5
95°	36.8	27.2	21.0	19.3
97.5°	44.8	36.3	31.2	30.6
100°	54.4	46.5	42.5	41.9
102.5°	65.7	58.4	55.0	53.8
105°	77.6	70.8	67.4	65.7
107.5°	90.1	83.3	79.9	78.2
110°	102.6	96.3	93.5	91.8

TEST NUMBER: P1012643

CATALOG NUMBER: S123RDIP-B560D585UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	115.0	108.8	106.0	104.3
115°	127.5	121.8	118.4	116.2
117.5°	138.8	133.7	130.9	128.1
120°	150.7	145.1	142.2	140.5
122.5°	162.0	155.8	153.0	151.3
125°	172.2	166.0	162.6	161.5
127.5°	181.3	175.1	171.1	169.4
130°	190.4	183.6	178.5	176.8
132.5°	198.9	190.4	184.7	182.4
135°	206.2	197.7	191.5	189.2
137.5°	213.0	204.0	197.7	195.5
140°	219.3	210.2	204.5	201.7
142.5°	224.9	217.0	210.8	208.5
145°	231.2	222.7	217.6	215.9
147.5°	236.8	229.5	224.4	223.2
150°	243.1	235.7	231.2	230.6
152.5°	248.7	242.5	238.0	238.0
155°	254.4	248.7	245.3	245.3
157.5°	259.5	254.4	251.6	251.0
160°	264.6	260.1	257.8	257.8
162.5°	268.0	264.6	262.9	262.9
165°	271.4	268.6	267.4	268.0
167.5°	274.2	272.0	271.4	272.0
170°	276.5	274.8	274.2	275.4
172.5°	278.2	277.1	277.1	277.6
175°	279.3	278.2	278.8	279.3
177.5°	279.9	279.3	279.9	280.5
180°	279.9	279.9	279.9	279.9

(END OF REPORT)