

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012653

Luminaire Tested: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012653
REPORT IS A COMBINATION OF REPORTS P993462 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D585UB35-4F0-XX-W2A-A1
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4254.0 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	45	45	45
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	53	51	50	45	45	45
2	91	84	78	73	84	78	73	68	67	63	60	56	54	51	47	45	43	39	39	39
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38	34	34	34
4	76	66	58	52	70	61	55	50	53	48	44	45	41	38	38	35	33	29	29	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26	26	26
6	65	53	45	40	60	50	43	38	43	38	34	37	33	30	32	28	26	23	23	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21	21	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	23	21	19	19	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	21	25	21	19	17	17	17
10	49	37	30	25	45	35	28	24	31	25	22	27	22	20	23	20	17	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9632	9632	9632	9632
5°	9639	11092	9663	8230
10°	9553	13390	9595	7188
15°	9456	15197	9456	6338
20°	9262	16392	9314	5622
25°	9119	15574	9102	5130
30°	8954	10791	8936	4649
35°	8756	6928	8716	4286
40°	8508	4892	8465	3925
45°	8078	3914	8066	3573
50°	7548	3275	7524	3162
55°	6954	2699	6898	2681
60°	6370	2231	6308	2280
65°	5686	1785	5722	1933
70°	5053	1240	5189	1562
75°	4283	921	4458	1201
80°	3409	611	3703	901
85°	2430	288	2651	561

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 12858 cd/sqm

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	2.1
10°-20°	275.1	6.5
20°-30°	433.2	10.2
30°-40°	450.5	10.6
40°-50°	385.4	9.1
50°-60°	293.8	6.9
60°-70°	188.2	4.4
70°-80°	90.2	2.1
80°-90°	25.3	0.6
90°-100°	47.0	1.1
100°-110°	142.4	3.3
110°-120°	242.3	5.7
120°-130°	318.8	7.5
130°-140°	358.4	8.4
140°-150°	352.3	8.3
150°-160°	296.6	7.0
160°-170°	197.5	4.6
170°-180°	69.1	1.6
0°-30°	796.2	18.7
0°-40°	1246.6	29.3
0°-60°	1925.8	45.3
0°-90°	2229.5	52.4
90°-120°	431.8	10.1
90°-150°	1461.2	34.3
90°-180°	2024.0	47.6
0°-180°	4254.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	895	895	895	895	895	
5°	894	1062	896	788	894	85
15°	854	1510	854	630	854	240
25°	777	1556	775	512	777	358
35°	678	675	675	418	678	424
45°	544	360	543	329	544	419
55°	384	226	381	224	384	344
65°	235	130	237	141	235	235
75°	113	55	117	72	113	122
85°	25	13	28	25	25	28
90°	1	17	1	17	1	4
95°	34	45	34	45	34	37
105°	129	137	129	137	129	138
115°	244	244	244	244	244	241
125°	357	353	357	353	357	318
135°	463	463	463	463	463	357
145°	562	562	562	562	562	351
155°	643	642	643	642	643	296
165°	701	698	701	698	701	198
175°	729	726	729	726	729	69
180°	731	731	731	731	731	

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8
2.5°	897.1	903.2	907.8	910.8	918.5	923.1	926.9	933.8	933.8	935.4	938.4
5°	894.0	907.0	916.2	928.5	944.6	952.2	962.9	972.1	985.2	992.0	998.9
7.5°	887.1	905.5	924.6	943.0	966.8	982.1	992.8	1016.6	1033.4	1054.1	1070.2
10°	877.9	903.2	927.7	956.0	988.2	1011.2	1027.3	1058.7	1090.9	1120.0	1144.5
12.5°	866.4	897.1	932.3	966.8	1012.0	1034.9	1061.0	1100.1	1146.0	1182.8	1215.7
15°	854.2	889.4	929.2	971.4	1028.1	1060.2	1097.8	1145.3	1196.6	1249.4	1294.6
17.5°	835.0	879.4	923.9	985.2	1051.8	1071.0	1103.1	1168.2	1231.8	1279.3	1334.5
20°	815.9	865.6	921.6	976.7	1048.7	1093.2	1123.0	1192.0	1260.2	1317.6	1370.5
22.5°	798.2	850.3	908.5	978.3	1045.7	1090.1	1127.6	1199.7	1278.6	1342.9	1408.0
25°	776.8	833.5	897.8	963.7	1045.7	1079.4	1120.7	1204.2	1287.7	1362.1	1442.5
27.5°	753.8	811.3	874.8	942.3	1017.3	1067.1	1107.7	1197.4	1299.2	1378.9	1461.6
30°	730.8	789.8	851.1	911.6	995.9	1043.4	1090.1	1188.9	1305.4	1396.5	1460.1
32.5°	708.6	758.4	818.9	877.9	961.4	1013.5	1066.4	1180.5	1307.7	1384.3	1414.9
35°	678.0	730.1	779.1	841.9	926.2	977.5	1039.5	1179.7	1297.7	1345.2	1329.9
37.5°	649.6	693.3	740.0	795.9	882.5	949.1	1013.5	1159.8	1264.8	1267.8	1181.3
40°	618.2	654.2	693.3	752.3	845.7	911.6	981.3	1129.2	1205.0	1159.8	1007.4
42.5°	582.2	614.4	645.0	702.5	804.4	877.9	953.0	1090.9	1118.4	1014.3	855.7
45°	543.9	569.9	598.3	658.8	760.7	833.5	908.5	1031.9	1003.5	856.5	705.5
47.5°	504.1	526.3	553.9	609.0	714.0	788.3	859.5	947.6	875.6	717.8	591.4
50°	464.2	481.9	508.7	565.4	666.5	733.9	799.8	857.2	756.1	615.9	488.7
52.5°	425.2	439.0	466.5	514.8	612.8	677.2	724.7	746.9	644.3	508.7	424.4
55°	383.8	399.1	417.5	466.5	563.8	611.3	642.7	642.0	536.2	431.3	350.9
57.5°	344.0	357.8	373.8	422.9	501.8	533.9	560.8	547.7	447.4	353.2	301.1
60°	308.7	316.4	334.0	375.4	435.1	462.7	478.0	455.8	365.4	298.0	249.0
62.5°	270.4	278.1	292.6	331.7	368.5	383.0	396.1	367.7	301.8	242.8	213.0
65°	235.2	245.1	254.3	285.7	305.7	323.3	321.7	298.0	235.9	197.6	173.1
67.5°	204.5	208.4	216.0	235.2	244.4	257.4	258.2	231.4	190.0	160.9	146.3
70°	171.6	175.4	180.8	190.0	196.1	199.2	197.6	173.9	143.3	125.6	112.6
72.5°	143.3	142.5	146.3	146.3	152.4	151.7	147.1	128.7	108.8	94.2	86.6
75°	112.6	113.4	114.1	112.6	110.3	107.2	103.4	89.6	76.6	69.7	62.8
77.5°	88.1	86.6	87.3	82.0	78.9	75.8	70.5	63.6	52.9	51.3	48.3
80°	62.8	62.1	61.3	59.0	52.1	49.0	45.2	41.4	39.1	37.5	36.8
82.5°	42.1	42.1	40.6	36.0	32.2	29.9	29.1	27.6	25.3	25.3	24.5
85°	25.3	24.5	23.0	18.4	16.1	16.1	16.1	16.1	14.6	14.6	13.8
87.5°	10.0	9.2	6.9	6.9	6.1	6.1	6.1	5.4	5.4	4.6	4.6
90°	0.6	1.9	3.1	4.4	5.7	6.3	7.1	8.8	10.5	12.1	13.8
92.5°	17.2	18.0	18.8	19.5	20.3	20.7	21.1	21.8	22.6	23.3	24.1
95°	33.9	34.8	35.7	36.6	37.5	37.9	38.4	39.4	40.5	41.5	42.5
97.5°	55.7	56.3	56.9	57.6	58.2	58.5	58.9	59.7	60.4	61.2	62.0
100°	78.1	78.9	79.6	80.4	81.1	81.5	81.8	82.5	83.1	83.8	84.4
102.5°	103.9	104.3	104.7	105.0	105.4	105.6	106.0	106.9	107.8	108.7	109.6
105°	129.1	129.4	129.6	129.9	130.2	130.3	130.9	132.0	133.2	134.3	135.5
107.5°	159.0	159.1	159.3	159.4	159.5	159.6	159.9	160.4	160.9	161.4	161.9
110°	186.5	186.8	187.0	187.3	187.6	187.7	187.8	188.1	188.3	188.6	188.8



TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	215.2	215.3	215.5	215.6	215.7	215.8	215.8	215.8	215.8	215.8	215.8
115°	243.9	244.3	244.7	245.0	245.4	245.6	245.5	245.2	245.0	244.7	244.5
117.5°	273.2	273.3	273.5	273.6	273.7	273.8	273.7	273.4	273.1	272.9	272.6
120°	300.2	301.0	301.7	302.5	303.2	303.6	303.3	302.6	302.0	301.3	300.7
122.5°	328.3	328.8	329.3	329.8	330.3	330.6	330.5	330.2	329.9	329.7	329.4
125°	357.0	357.4	357.8	358.1	358.5	358.7	358.6	358.3	358.1	357.8	357.6
127.5°	383.4	384.2	384.9	385.7	386.4	386.8	386.7	386.4	386.2	385.9	385.7
130°	409.8	410.8	411.8	412.9	413.9	414.4	414.2	413.8	413.5	413.1	412.7
132.5°	436.2	437.2	438.2	439.3	440.3	440.8	440.7	440.4	440.1	439.9	439.6
135°	463.2	464.0	464.7	465.5	466.2	466.6	466.5	466.4	466.3	466.1	466.0
137.5°	487.9	488.5	489.1	489.8	490.4	490.7	490.9	491.3	491.6	492.0	492.4
140°	513.7	514.3	515.0	515.6	516.3	516.6	516.7	516.8	516.9	517.0	517.1
142.5°	537.2	537.8	538.5	539.1	539.8	540.1	540.2	540.5	540.7	541.0	541.2
145°	561.9	562.1	562.4	562.6	562.9	563.0	563.2	563.6	564.0	564.4	564.8
147.5°	583.1	583.6	584.1	584.6	585.1	585.4	585.6	586.0	586.3	586.7	587.1
150°	605.5	605.8	606.0	606.3	606.6	606.7	606.8	607.1	607.3	607.6	607.8
152.5°	623.9	624.3	624.7	625.0	625.4	625.6	625.7	625.8	625.9	626.1	626.2
155°	643.4	643.4	643.4	643.4	643.4	643.4	643.5	643.6	643.7	643.9	644.0
157.5°	660.0	659.9	659.8	659.7	659.6	659.5	659.6	659.7	659.8	659.9	660.0
160°	675.5	675.3	675.0	674.8	674.5	674.4	674.4	674.4	674.4	674.4	674.4
162.5°	689.3	688.9	688.5	688.2	687.8	687.6	687.7	687.8	687.9	688.1	688.2
165°	700.8	700.4	700.0	699.7	699.3	699.1	699.1	699.1	699.1	699.1	699.1
167.5°	710.5	710.0	709.5	709.0	708.5	708.3	708.4	708.5	708.6	708.7	708.8
170°	718.6	718.1	717.6	717.1	716.6	716.3	716.3	716.3	716.3	716.3	716.3
172.5°	724.9	724.4	723.9	723.4	722.9	722.6	722.6	722.6	722.6	722.6	722.6
175°	728.9	728.4	727.9	727.4	726.9	726.6	726.6	726.6	726.6	726.6	726.6
177.5°	731.2	730.7	730.2	729.7	729.2	728.9	728.9	728.9	728.9	728.9	728.9
180°	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8
2.5°	944.6	944.6	951.4	958.3	954.5	956.8	965.2	962.2	968.3	967.5	969.8
5°	1015.8	1024.2	1031.1	1045.7	1048.0	1045.7	1060.2	1064.1	1071.0	1062.5	1066.4
7.5°	1096.2	1113.9	1130.7	1152.2	1159.1	1160.6	1168.2	1179.0	1188.2	1171.3	1179.7
10°	1174.4	1201.2	1235.7	1254.8	1271.7	1277.8	1283.9	1290.8	1301.5	1311.5	1303.8
12.5°	1258.6	1297.7	1330.6	1365.1	1385.8	1383.5	1401.1	1405.7	1414.1	1416.4	1419.5
15°	1327.6	1382.7	1403.4	1454.7	1459.3	1474.7	1494.6	1512.2	1514.5	1509.9	1509.9
17.5°	1393.5	1441.0	1477.7	1519.1	1527.5	1540.5	1565.8	1574.3	1577.3	1576.6	1576.6
20°	1447.1	1478.5	1540.5	1575.0	1588.8	1605.7	1623.3	1634.0	1636.3	1639.4	1634.8
22.5°	1482.3	1529.8	1580.4	1608.7	1620.2	1626.3	1637.8	1640.9	1637.1	1637.8	1638.6
25°	1509.9	1556.6	1587.3	1594.9	1594.2	1586.5	1578.1	1563.5	1562.0	1555.9	1543.6
27.5°	1517.6	1535.2	1531.4	1499.9	1468.5	1465.5	1414.9	1387.3	1355.9	1360.5	1342.9
30°	1476.2	1453.2	1398.8	1319.2	1286.2	1232.6	1175.9	1116.9	1093.9	1068.7	1115.4
32.5°	1375.1	1293.1	1196.6	1093.2	1038.0	990.5	930.0	887.1	862.6	841.9	881.7
35°	1222.6	1094.7	966.8	868.7	823.5	780.6	723.9	702.5	671.8	674.9	678.7
37.5°	1026.5	885.6	789.0	692.5	662.6	645.0	603.7	570.7	560.0	556.9	556.9
40°	842.7	727.0	641.2	565.4	542.4	527.8	494.9	479.6	468.1	465.0	468.8
42.5°	697.1	598.3	531.6	481.1	465.0	446.6	432.8	413.7	411.4	406.0	412.9
45°	585.3	499.5	449.7	412.9	399.1	392.2	376.9	365.4	360.8	360.0	365.4
47.5°	496.4	429.8	386.1	363.1	352.4	345.5	332.5	327.9	323.3	324.8	322.5
50°	416.7	366.9	338.6	317.9	311.0	304.1	295.7	291.1	288.8	288.8	288.0
52.5°	357.8	316.4	298.0	278.8	275.8	272.0	262.8	259.7	255.9	255.1	258.2
55°	306.4	278.1	259.7	248.2	245.1	237.5	233.6	229.8	227.5	226.0	226.8
57.5°	262.0	240.5	228.3	218.3	213.0	209.9	203.0	202.2	200.7	200.7	199.9
60°	225.2	209.9	195.3	189.2	185.4	181.6	180.8	176.2	173.9	175.4	174.7
62.5°	190.7	178.5	170.1	163.2	160.9	157.8	155.5	154.0	151.7	152.4	152.4
65°	159.3	149.4	143.3	137.1	136.4	133.3	132.5	131.0	131.0	130.2	131.8
67.5°	131.0	124.1	118.7	114.9	112.6	113.4	110.3	108.0	108.0	107.2	109.5
70°	104.2	100.4	95.0	90.4	87.3	87.3	83.5	82.7	82.7	82.7	82.0
72.5°	80.4	73.5	71.2	69.7	69.7	69.7	68.2	68.2	67.4	68.2	67.4
75°	59.8	59.0	57.5	56.7	56.7	55.9	55.2	55.2	55.2	55.2	55.2
77.5°	46.7	46.7	45.2	44.4	44.4	44.4	43.7	43.7	42.9	42.9	42.9
80°	34.5	34.5	32.9	32.9	32.9	32.2	32.2	32.2	32.9	32.2	32.2
82.5°	23.7	23.7	23.0	23.7	23.0	22.2	22.2	22.2	21.4	22.2	22.2
85°	13.8	13.8	13.0	12.3	13.0	13.0	12.3	13.0	12.3	13.0	12.3
87.5°	5.4	4.6	4.6	4.6	3.8	4.6	3.8	3.8	4.6	3.8	4.6
90°	14.3	14.8	15.3	15.8	16.1	16.2	16.5	16.7	17.0	17.2	17.0
92.5°	24.5	24.9	25.2	25.6	25.8	25.7	25.4	25.2	24.9	24.7	24.9
95°	43.0	43.5	44.0	44.5	44.8	44.8	44.8	44.8	44.8	44.8	44.8
97.5°	62.6	63.3	63.9	64.6	64.9	64.8	64.7	64.6	64.4	64.3	64.4
100°	84.8	85.2	85.5	85.9	86.1	86.2	86.5	86.7	87.0	87.2	87.0
102.5°	110.0	110.4	110.7	111.1	111.3	111.2	111.1	111.0	110.9	110.8	110.9
105°	135.5	135.5	135.5	135.5	135.5	135.6	135.9	136.1	136.4	136.6	136.4
107.5°	162.3	162.7	163.0	163.4	163.6	163.5	163.4	163.3	163.1	163.0	163.1
110°	189.3	189.8	190.3	190.8	191.1	191.0	190.7	190.5	190.2	190.0	190.2



TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	216.4	217.1	217.7	218.4	218.7	218.7	218.7	218.7	218.7	218.7	218.7
115°	244.6	244.8	244.9	245.0	245.1	245.0	244.9	244.8	244.6	244.5	244.6
117.5°	272.6	272.6	272.6	272.6	272.6	272.4	272.0	271.7	271.3	270.9	271.3
120°	300.6	300.5	300.4	300.3	300.2	300.1	299.8	299.5	299.3	299.0	299.3
122.5°	329.0	328.6	328.3	327.9	327.7	327.5	327.1	326.8	326.4	326.0	326.4
125°	357.1	356.6	356.1	355.6	355.3	355.0	354.5	354.0	353.5	353.0	353.5
127.5°	384.9	384.1	383.4	382.6	382.2	382.0	381.5	381.0	380.5	380.0	380.5
130°	412.2	411.7	411.2	410.7	410.4	410.0	409.1	408.2	407.3	406.4	407.3
132.5°	439.0	438.4	437.7	437.1	436.8	436.5	435.8	435.2	434.5	433.9	434.5
135°	465.5	465.0	464.5	464.0	463.7	463.6	463.3	463.1	462.8	462.6	462.8
137.5°	491.8	491.2	490.5	489.9	489.6	489.4	489.0	488.7	488.3	487.9	488.3
140°	517.0	516.9	516.8	516.7	516.6	516.1	515.2	514.3	513.4	512.5	513.4
142.5°	541.1	541.0	540.9	540.8	540.7	540.4	539.7	539.1	538.4	537.8	538.4
145°	564.7	564.5	564.4	564.3	564.2	563.9	563.4	562.9	562.4	561.9	562.4
147.5°	587.1	587.1	587.1	587.1	587.1	586.7	586.0	585.2	584.5	583.7	584.5
150°	607.8	607.8	607.8	607.8	607.8	607.4	606.7	605.9	605.2	604.4	605.2
152.5°	626.4	626.7	626.9	627.2	627.3	627.0	626.4	625.7	625.1	624.5	625.1
155°	644.5	645.0	645.5	646.0	646.3	645.8	644.9	644.0	643.1	642.2	643.1
157.5°	660.5	661.0	661.5	662.0	662.3	661.9	661.2	660.4	659.7	658.9	659.7
160°	675.0	675.7	676.3	677.0	677.3	677.0	676.5	676.0	675.5	675.0	675.5
162.5°	688.8	689.4	690.1	690.7	691.0	690.6	689.7	688.8	687.9	687.0	687.9
165°	699.9	700.6	701.4	702.1	702.5	702.1	701.2	700.3	699.4	698.5	699.4
167.5°	709.6	710.4	711.1	711.9	712.3	711.9	711.1	710.4	709.6	708.8	709.6
170°	717.2	718.1	719.0	719.9	720.3	719.9	719.0	718.1	717.2	716.3	717.2
172.5°	723.4	724.1	724.9	725.6	726.0	725.6	724.7	723.8	722.9	722.0	722.9
175°	727.4	728.2	728.9	729.7	730.1	729.6	728.7	727.8	726.9	726.0	726.9
177.5°	729.7	730.5	731.2	732.0	732.4	731.9	731.0	730.1	729.2	728.3	729.2
180°	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8
2.5°	966.0	961.4	958.3	956.0	953.7	960.6	951.4	941.5	934.6	930.0	928.5
5°	1067.1	1057.2	1048.7	1041.8	1043.4	1043.4	1027.3	1009.7	994.3	985.9	976.7
7.5°	1184.3	1173.6	1156.8	1152.9	1149.9	1130.7	1114.6	1082.4	1063.3	1044.1	1027.3
10°	1300.8	1287.0	1270.9	1265.5	1257.9	1234.1	1209.6	1168.2	1144.5	1109.3	1087.0
12.5°	1409.6	1392.7	1376.6	1372.8	1361.3	1340.6	1298.5	1255.6	1215.0	1177.4	1138.4
15°	1500.7	1496.1	1471.6	1456.3	1431.0	1402.7	1393.5	1335.2	1283.9	1244.8	1174.4
17.5°	1577.3	1555.9	1532.9	1522.9	1513.0	1480.0	1447.1	1387.3	1332.2	1274.7	1229.5
20°	1638.6	1614.9	1598.8	1584.2	1579.6	1542.1	1490.0	1437.1	1376.6	1312.3	1253.3
22.5°	1641.7	1638.6	1627.9	1619.5	1610.3	1585.7	1544.4	1478.5	1414.1	1343.7	1266.3
25°	1578.1	1573.5	1604.1	1596.5	1602.6	1593.4	1571.2	1516.0	1441.0	1358.2	1280.1
27.5°	1386.6	1433.3	1481.6	1498.4	1509.9	1542.8	1553.6	1522.9	1462.4	1374.3	1287.0
30°	1126.1	1188.2	1266.3	1308.4	1340.6	1401.9	1481.6	1491.5	1463.2	1392.7	1285.5
32.5°	884.0	940.7	1003.5	1053.3	1096.2	1221.9	1329.1	1406.5	1420.3	1383.5	1289.3
35°	712.4	737.0	796.7	844.2	902.4	1009.7	1136.1	1260.9	1345.2	1349.8	1277.8
37.5°	587.6	600.6	652.7	679.5	714.0	808.2	926.2	1089.3	1220.3	1282.4	1245.6
40°	486.4	516.3	546.2	561.5	586.0	651.2	764.5	892.5	1054.9	1169.8	1195.8
42.5°	422.1	435.1	454.3	475.7	491.0	547.7	623.6	740.8	887.1	1047.2	1119.2
45°	372.3	376.9	396.8	410.6	426.7	466.5	520.2	618.2	746.9	904.7	1027.3
47.5°	330.9	340.1	350.9	359.3	370.0	400.6	446.6	517.9	631.2	772.2	904.0
50°	294.2	299.5	313.3	317.1	324.8	346.3	381.5	435.9	529.3	642.0	778.3
52.5°	259.7	269.7	275.0	280.4	287.3	304.9	327.9	372.3	442.8	548.5	664.2
55°	232.9	235.9	243.6	248.2	253.6	265.8	285.7	318.7	373.8	458.1	567.7
57.5°	206.8	206.8	214.5	218.3	223.7	232.9	250.5	275.8	315.6	378.4	478.8
60°	179.3	180.0	186.2	190.7	192.3	201.5	216.0	235.9	266.6	312.6	394.5
62.5°	154.7	158.6	161.6	163.2	168.5	173.9	186.2	199.9	221.4	262.0	320.2
65°	134.1	134.8	137.1	138.7	141.0	147.1	156.3	165.5	183.9	213.7	261.2
67.5°	110.3	113.4	116.4	116.4	118.7	121.8	131.0	138.7	152.4	170.1	202.2
70°	82.7	84.3	88.9	91.2	94.2	99.6	104.2	108.8	119.5	132.5	157.0
72.5°	68.9	68.9	70.5	71.2	71.2	75.1	82.0	86.6	91.9	101.1	118.0
75°	55.2	55.2	57.5	56.7	58.2	59.8	60.5	63.6	66.6	73.5	83.5
77.5°	43.7	44.4	44.4	45.2	45.2	46.0	46.7	48.3	49.8	53.6	58.2
80°	32.2	32.9	32.9	33.7	33.7	34.5	35.2	36.0	37.5	39.1	41.4
82.5°	22.2	23.0	23.0	23.7	23.0	23.7	24.5	24.5	25.3	26.8	27.6
85°	13.0	13.0	13.8	13.0	13.0	13.0	13.8	13.8	14.6	16.9	16.9
87.5°	3.8	4.6	3.8	4.6	4.6	4.6	4.6	5.4	5.4	6.1	6.9
90°	16.7	16.5	16.2	16.1	15.8	15.3	14.8	14.3	13.8	12.1	10.5
92.5°	25.2	25.4	25.7	25.8	25.6	25.2	24.9	24.5	24.1	23.3	22.6
95°	44.8	44.8	44.8	44.8	44.5	44.0	43.5	43.0	42.5	41.5	40.5
97.5°	64.6	64.7	64.8	64.9	64.6	63.9	63.3	62.6	62.0	61.2	60.4
100°	86.7	86.5	86.2	86.1	85.9	85.5	85.2	84.8	84.4	83.8	83.1
102.5°	111.0	111.1	111.2	111.3	111.1	110.7	110.4	110.0	109.6	108.7	107.8
105°	136.1	135.9	135.6	135.5	135.5	135.5	135.5	135.5	135.5	134.3	133.2
107.5°	163.3	163.4	163.5	163.6	163.4	163.0	162.7	162.3	161.9	161.4	160.9
110°	190.5	190.7	191.0	191.1	190.8	190.3	189.8	189.3	188.8	188.6	188.3

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	218.7	218.7	218.7	218.7	218.4	217.7	217.1	216.4	215.8	215.8	215.8
115°	244.8	244.9	245.0	245.1	245.0	244.9	244.8	244.6	244.5	244.7	245.0
117.5°	271.7	272.0	272.4	272.6	272.6	272.6	272.6	272.6	272.6	272.9	273.1
120°	299.5	299.8	300.1	300.2	300.3	300.4	300.5	300.6	300.7	301.3	302.0
122.5°	326.8	327.1	327.5	327.7	327.9	328.3	328.6	329.0	329.4	329.7	329.9
125°	354.0	354.5	355.0	355.3	355.6	356.1	356.6	357.1	357.6	357.8	358.1
127.5°	381.0	381.5	382.0	382.2	382.6	383.4	384.1	384.9	385.7	385.9	386.2
130°	408.2	409.1	410.0	410.4	410.7	411.2	411.7	412.2	412.7	413.1	413.5
132.5°	435.2	435.8	436.5	436.8	437.1	437.7	438.4	439.0	439.6	439.9	440.1
135°	463.1	463.3	463.6	463.7	464.0	464.5	465.0	465.5	466.0	466.1	466.3
137.5°	488.7	489.0	489.4	489.6	489.9	490.5	491.2	491.8	492.4	492.0	491.6
140°	514.3	515.2	516.1	516.6	516.7	516.8	516.9	517.0	517.1	517.0	516.9
142.5°	539.1	539.7	540.4	540.7	540.8	540.9	541.0	541.1	541.2	541.0	540.7
145°	562.9	563.4	563.9	564.2	564.3	564.4	564.5	564.7	564.8	564.4	564.0
147.5°	585.2	586.0	586.7	587.1	587.1	587.1	587.1	587.1	587.1	586.7	586.3
150°	605.9	606.7	607.4	607.8	607.8	607.8	607.8	607.8	607.8	607.6	607.3
152.5°	625.7	626.4	627.0	627.3	627.2	626.9	626.7	626.4	626.2	626.1	625.9
155°	644.0	644.9	645.8	646.3	646.0	645.5	645.0	644.5	644.0	643.9	643.7
157.5°	660.4	661.2	661.9	662.3	662.0	661.5	661.0	660.5	660.0	659.9	659.8
160°	676.0	676.5	677.0	677.3	677.0	676.3	675.7	675.0	674.4	674.4	674.4
162.5°	688.8	689.7	690.6	691.0	690.7	690.1	689.4	688.8	688.2	688.1	687.9
165°	700.3	701.2	702.1	702.5	702.1	701.4	700.6	699.9	699.1	699.1	699.1
167.5°	710.4	711.1	711.9	712.3	711.9	711.1	710.4	709.6	708.8	708.7	708.6
170°	718.1	719.0	719.9	720.3	719.9	719.0	718.1	717.2	716.3	716.3	716.3
172.5°	723.8	724.7	725.6	726.0	725.6	724.9	724.1	723.4	722.6	722.6	722.6
175°	727.8	728.7	729.6	730.1	729.7	728.9	728.2	727.4	726.6	726.6	726.6
177.5°	730.1	731.0	731.9	732.4	732.0	731.2	730.5	729.7	728.9	728.9	728.9
180°	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8
2.5°	926.2	922.3	918.5	918.5	910.1	902.4	898.6	900.1	895.5	889.4	883.3
5°	966.8	951.4	948.4	940.0	928.5	912.4	904.0	896.3	887.1	874.8	863.4
7.5°	1004.3	984.4	973.7	965.2	943.0	920.8	902.4	890.2	874.1	855.7	841.9
10°	1053.3	1016.6	1005.1	985.9	954.5	923.1	901.7	881.7	859.5	838.1	819.7
12.5°	1092.4	1050.3	1028.8	1009.7	969.1	929.2	893.2	868.7	841.9	818.2	794.4
15°	1136.8	1089.3	1051.8	1028.8	977.5	929.2	888.6	854.2	824.3	795.2	774.5
17.5°	1158.3	1098.5	1081.7	1048.7	974.4	926.2	876.4	839.6	803.6	769.9	745.4
20°	1192.0	1122.3	1080.1	1057.9	992.0	920.8	862.6	820.5	782.9	746.9	720.9
22.5°	1194.3	1118.4	1090.9	1048.7	967.5	904.7	850.3	799.0	755.3	721.6	694.8
25°	1188.9	1111.6	1073.3	1039.5	972.1	895.5	825.8	775.3	732.4	693.3	661.9
27.5°	1186.6	1091.6	1055.6	1021.9	946.1	868.7	811.3	753.8	704.8	670.3	638.1
30°	1183.6	1070.2	1026.5	987.5	917.7	848.0	779.1	729.3	682.6	638.9	606.7
32.5°	1163.6	1041.1	996.6	955.3	880.2	810.5	756.1	703.2	652.7	612.1	583.0
35°	1157.5	1014.3	956.0	911.6	838.1	776.0	718.6	674.9	627.4	586.8	552.3
37.5°	1139.9	986.7	923.9	867.2	790.6	731.6	689.5	645.8	599.8	556.2	528.6
40°	1109.3	954.5	883.3	825.0	746.1	686.4	647.3	615.1	569.9	530.9	497.2
42.5°	1064.1	921.6	845.0	783.7	696.3	640.4	608.3	577.6	539.3	498.7	471.1
45°	1012.0	877.9	806.7	738.5	649.6	595.2	561.5	543.1	507.9	473.4	441.3
47.5°	940.7	832.7	762.2	691.8	601.4	548.5	521.7	503.3	478.8	441.3	415.2
50°	851.1	774.5	707.8	645.0	553.9	503.3	476.5	462.7	442.0	415.2	389.9
52.5°	751.5	707.1	651.9	593.7	505.6	458.1	433.6	422.9	407.5	382.3	360.8
55°	651.2	632.0	594.5	537.0	455.0	416.0	394.5	380.7	369.2	350.9	332.5
57.5°	561.5	552.3	526.3	481.9	412.9	372.3	353.9	344.7	335.5	321.7	303.4
60°	468.8	478.8	452.0	429.8	366.9	331.7	315.6	305.7	301.1	288.8	277.3
62.5°	388.4	397.6	382.3	365.4	321.0	289.6	279.6	270.4	267.4	256.6	245.1
65°	315.6	327.1	315.6	306.4	279.6	253.6	241.3	236.7	233.6	226.8	217.6
67.5°	251.3	262.8	257.4	245.9	237.5	216.0	209.1	204.5	203.0	197.6	190.0
70°	189.2	205.3	206.8	199.9	192.3	182.3	177.7	176.2	172.4	167.8	163.2
72.5°	136.4	154.7	155.5	155.5	150.9	150.9	146.3	144.0	144.0	139.4	134.1
75°	100.4	112.6	114.1	115.7	118.0	120.3	117.2	117.2	116.4	111.8	109.5
77.5°	66.6	77.4	81.2	86.6	89.6	89.6	91.2	92.7	91.2	88.9	87.3
80°	42.9	50.6	55.2	58.2	62.8	65.1	67.4	68.2	66.6	65.9	63.6
82.5°	28.3	30.6	32.9	36.8	42.1	46.0	46.0	45.2	46.7	46.0	45.2
85°	16.1	17.6	18.4	19.2	22.2	26.0	26.8	27.6	29.1	27.6	26.0
87.5°	6.1	6.9	6.9	6.9	8.4	9.2	11.5	14.6	13.8	12.3	12.3
90°	8.8	7.1	6.3	5.7	4.4	3.1	1.9	0.6	1.9	3.1	4.4
92.5°	21.8	21.1	20.7	20.3	19.5	18.8	18.0	17.2	18.0	18.8	19.5
95°	39.4	38.4	37.9	37.5	36.6	35.7	34.8	33.9	34.8	35.7	36.6
97.5°	59.7	58.9	58.5	58.2	57.6	56.9	56.3	55.7	56.3	56.9	57.6
100°	82.5	81.8	81.5	81.1	80.4	79.6	78.9	78.1	78.9	79.6	80.4
102.5°	106.9	106.0	105.6	105.4	105.0	104.7	104.3	103.9	104.3	104.7	105.0
105°	132.0	130.9	130.3	130.2	129.9	129.6	129.4	129.1	129.4	129.6	129.9
107.5°	160.4	159.9	159.6	159.5	159.4	159.3	159.1	159.0	159.1	159.3	159.4
110°	188.1	187.8	187.7	187.6	187.3	187.0	186.8	186.5	186.8	187.0	187.3

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	215.8	215.8	215.8	215.7	215.6	215.5	215.3	215.2	215.3	215.5	215.6
115°	245.2	245.5	245.6	245.4	245.0	244.7	244.3	243.9	244.3	244.7	245.0
117.5°	273.4	273.7	273.8	273.7	273.6	273.5	273.3	273.2	273.3	273.5	273.6
120°	302.6	303.3	303.6	303.2	302.5	301.7	301.0	300.2	301.0	301.7	302.5
122.5°	330.2	330.5	330.6	330.3	329.8	329.3	328.8	328.3	328.8	329.3	329.8
125°	358.3	358.6	358.7	358.5	358.1	357.8	357.4	357.0	357.4	357.8	358.1
127.5°	386.4	386.7	386.8	386.4	385.7	384.9	384.2	383.4	384.2	384.9	385.7
130°	413.8	414.2	414.4	413.9	412.9	411.8	410.8	409.8	410.8	411.8	412.9
132.5°	440.4	440.7	440.8	440.3	439.3	438.2	437.2	436.2	437.2	438.2	439.3
135°	466.4	466.5	466.6	466.2	465.5	464.7	464.0	463.2	464.0	464.7	465.5
137.5°	491.3	490.9	490.7	490.4	489.8	489.1	488.5	487.9	488.5	489.1	489.8
140°	516.8	516.7	516.6	516.3	515.6	515.0	514.3	513.7	514.3	515.0	515.6
142.5°	540.5	540.2	540.1	539.8	539.1	538.5	537.8	537.2	537.8	538.5	539.1
145°	563.6	563.2	563.0	562.9	562.6	562.4	562.1	561.9	562.1	562.4	562.6
147.5°	586.0	585.6	585.4	585.1	584.6	584.1	583.6	583.1	583.6	584.1	584.6
150°	607.1	606.8	606.7	606.6	606.3	606.0	605.8	605.5	605.8	606.0	606.3
152.5°	625.8	625.7	625.6	625.4	625.0	624.7	624.3	623.9	624.3	624.7	625.0
155°	643.6	643.5	643.4	643.4	643.4	643.4	643.4	643.4	643.4	643.4	643.4
157.5°	659.7	659.6	659.5	659.6	659.7	659.8	659.9	660.0	659.9	659.8	659.7
160°	674.4	674.4	674.4	674.5	674.8	675.0	675.3	675.5	675.3	675.0	674.8
162.5°	687.8	687.7	687.6	687.8	688.2	688.5	688.9	689.3	688.9	688.5	688.2
165°	699.1	699.1	699.1	699.3	699.7	700.0	700.4	700.8	700.4	700.0	699.7
167.5°	708.5	708.4	708.3	708.5	709.0	709.5	710.0	710.5	710.0	709.5	709.0
170°	716.3	716.3	716.3	716.6	717.1	717.6	718.1	718.6	718.1	717.6	717.1
172.5°	722.6	722.6	722.6	722.9	723.4	723.9	724.4	724.9	724.4	723.9	723.4
175°	726.6	726.6	726.6	726.9	727.4	727.9	728.4	728.9	728.4	727.9	727.4
177.5°	728.9	728.9	728.9	729.2	729.7	730.2	730.7	731.2	730.7	730.2	729.7
180°	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8
2.5°	883.3	879.4	877.9	874.1	864.9	858.8	851.9	847.3	848.0	844.2	846.5
5°	855.7	854.9	849.6	841.9	828.9	822.0	809.7	803.6	800.5	801.3	796.7
7.5°	832.7	825.8	822.0	809.7	797.5	782.9	773.0	767.6	763.0	758.4	755.3
10°	806.7	800.5	794.4	781.4	764.5	750.7	737.0	731.6	724.7	721.6	719.3
12.5°	779.1	775.3	767.6	752.3	733.1	720.1	704.0	700.9	691.8	685.6	684.1
15°	753.8	751.5	737.7	720.1	700.9	687.9	674.1	664.9	649.6	652.7	647.3
17.5°	727.0	717.0	708.6	684.9	675.7	655.7	639.7	635.1	624.3	617.4	610.6
20°	697.1	691.0	680.3	664.9	642.7	619.7	607.5	599.8	593.7	583.0	579.9
22.5°	668.8	661.1	651.9	632.0	612.8	593.7	576.8	569.9	562.3	554.6	550.0
25°	646.6	635.1	625.1	600.6	581.4	565.4	554.6	543.1	532.4	527.8	526.3
27.5°	612.1	605.2	595.2	572.2	554.6	537.0	527.0	519.4	507.9	502.5	497.9
30°	589.9	576.1	564.6	546.2	528.6	509.4	500.2	491.0	484.2	477.3	471.9
32.5°	560.0	549.3	540.1	521.7	504.1	486.4	476.5	462.7	458.9	453.5	447.4
35°	530.9	524.0	514.0	494.1	475.0	462.7	452.0	439.0	434.4	430.5	425.2
37.5°	503.3	493.3	486.4	467.3	450.4	435.9	427.5	416.7	413.7	409.1	405.2
40°	479.6	469.6	462.7	443.5	425.9	410.6	405.2	394.5	389.9	384.6	382.3
42.5°	452.7	444.3	435.1	421.3	402.9	387.6	376.9	370.8	364.6	362.3	357.8
45°	424.4	416.7	409.8	394.5	375.4	364.6	355.5	347.0	342.4	338.6	335.5
47.5°	399.9	393.0	383.8	366.9	351.6	341.7	332.5	324.0	319.4	314.9	311.0
50°	371.5	367.7	357.8	341.7	327.1	315.6	307.2	299.5	296.5	291.1	285.0
52.5°	346.3	339.4	330.9	317.9	304.9	291.1	279.6	275.0	269.7	266.6	261.2
55°	316.4	311.8	302.6	291.1	277.3	265.8	257.4	251.3	244.4	241.3	234.4
57.5°	291.1	282.7	278.1	263.5	250.5	239.0	232.9	226.8	219.1	214.5	211.4
60°	263.5	255.9	249.0	236.7	227.5	215.3	206.1	200.7	195.3	189.2	186.2
62.5°	236.7	230.6	222.2	212.2	200.7	190.7	183.9	176.2	173.1	167.0	164.7
65°	207.6	203.0	196.1	184.6	175.4	167.0	160.1	154.0	150.9	148.6	147.1
67.5°	181.6	175.4	170.8	160.9	150.9	144.0	140.2	136.4	132.5	130.2	127.9
70°	154.7	150.1	145.6	136.4	129.5	123.3	120.3	117.2	114.9	112.6	110.3
72.5°	127.2	124.9	120.3	114.1	108.8	104.2	101.9	98.1	95.8	91.9	90.4
75°	105.0	101.1	98.8	93.5	88.9	85.0	82.0	77.4	74.3	72.8	72.0
77.5°	82.7	81.2	78.1	73.5	71.2	67.4	62.8	61.3	59.8	59.8	59.0
80°	62.1	59.8	57.5	53.6	51.3	48.3	48.3	48.3	47.5	48.3	47.5
82.5°	42.1	40.6	39.1	36.8	36.0	36.0	36.8	36.8	36.8	36.8	36.8
85°	24.5	24.5	24.5	25.3	24.5	24.5	25.3	26.0	25.3	25.3	24.5
87.5°	11.5	11.5	12.3	12.3	13.0	13.0	13.0	13.0	13.0	13.0	13.8
90°	5.7	6.3	7.1	8.8	10.5	12.1	13.8	14.3	14.8	15.3	15.8
92.5°	20.3	20.7	21.1	21.8	22.6	23.3	24.1	24.5	24.9	25.2	25.6
95°	37.5	37.9	38.4	39.4	40.5	41.5	42.5	43.0	43.5	44.0	44.5
97.5°	58.2	58.5	58.9	59.7	60.4	61.2	62.0	62.6	63.3	63.9	64.6
100°	81.1	81.5	81.8	82.5	83.1	83.8	84.4	84.8	85.2	85.5	85.9
102.5°	105.4	105.6	106.0	106.9	107.8	108.7	109.6	110.0	110.4	110.7	111.1
105°	130.2	130.3	130.9	132.0	133.2	134.3	135.5	135.5	135.5	135.5	135.5
107.5°	159.5	159.6	159.9	160.4	160.9	161.4	161.9	162.3	162.7	163.0	163.4
110°	187.6	187.7	187.8	188.1	188.3	188.6	188.8	189.3	189.8	190.3	190.8

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	215.7	215.8	215.8	215.8	215.8	215.8	215.8	216.4	217.1	217.7	218.4
115°	245.4	245.6	245.5	245.2	245.0	244.7	244.5	244.6	244.8	244.9	245.0
117.5°	273.7	273.8	273.7	273.4	273.1	272.9	272.6	272.6	272.6	272.6	272.6
120°	303.2	303.6	303.3	302.6	302.0	301.3	300.7	300.6	300.5	300.4	300.3
122.5°	330.3	330.6	330.5	330.2	329.9	329.7	329.4	329.0	328.6	328.3	327.9
125°	358.5	358.7	358.6	358.3	358.1	357.8	357.6	357.1	356.6	356.1	355.6
127.5°	386.4	386.8	386.7	386.4	386.2	385.9	385.7	384.9	384.1	383.4	382.6
130°	413.9	414.4	414.2	413.8	413.5	413.1	412.7	412.2	411.7	411.2	410.7
132.5°	440.3	440.8	440.7	440.4	440.1	439.9	439.6	439.0	438.4	437.7	437.1
135°	466.2	466.6	466.5	466.4	466.3	466.1	466.0	465.5	465.0	464.5	464.0
137.5°	490.4	490.7	490.9	491.3	491.6	492.0	492.4	491.8	491.2	490.5	489.9
140°	516.3	516.6	516.7	516.8	516.9	517.0	517.1	517.0	516.9	516.8	516.7
142.5°	539.8	540.1	540.2	540.5	540.7	541.0	541.2	541.1	541.0	540.9	540.8
145°	562.9	563.0	563.2	563.6	564.0	564.4	564.8	564.7	564.5	564.4	564.3
147.5°	585.1	585.4	585.6	586.0	586.3	586.7	587.1	587.1	587.1	587.1	587.1
150°	606.6	606.7	606.8	607.1	607.3	607.6	607.8	607.8	607.8	607.8	607.8
152.5°	625.4	625.6	625.7	625.8	625.9	626.1	626.2	626.4	626.7	626.9	627.2
155°	643.4	643.4	643.5	643.6	643.7	643.9	644.0	644.5	645.0	645.5	646.0
157.5°	659.6	659.5	659.6	659.7	659.8	659.9	660.0	660.5	661.0	661.5	662.0
160°	674.5	674.4	674.4	674.4	674.4	674.4	674.4	675.0	675.7	676.3	677.0
162.5°	687.8	687.6	687.7	687.8	687.9	688.1	688.2	688.8	689.4	690.1	690.7
165°	699.3	699.1	699.1	699.1	699.1	699.1	699.1	699.9	700.6	701.4	702.1
167.5°	708.5	708.3	708.4	708.5	708.6	708.7	708.8	709.6	710.4	711.1	711.9
170°	716.6	716.3	716.3	716.3	716.3	716.3	716.3	717.2	718.1	719.0	719.9
172.5°	722.9	722.6	722.6	722.6	722.6	722.6	722.6	723.4	724.1	724.9	725.6
175°	726.9	726.6	726.6	726.6	726.6	726.6	726.6	727.4	728.2	728.9	729.7
177.5°	729.2	728.9	728.9	728.9	728.9	728.9	728.9	729.7	730.5	731.2	732.0
180°	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8
2.5°	845.7	846.5	844.2	839.6	838.8	840.4	845.0	843.4	839.6	846.5	840.4
5°	799.0	795.2	793.6	795.2	790.6	788.3	792.9	790.6	792.9	793.6	795.9
7.5°	753.8	754.6	750.0	750.7	744.6	746.1	746.1	746.1	748.4	750.0	753.0
10°	714.7	716.3	710.9	711.7	707.1	704.0	706.3	710.9	710.9	710.9	712.4
12.5°	683.3	676.4	672.6	671.8	666.5	664.9	669.5	671.1	674.9	674.9	677.2
15°	644.3	642.7	639.7	639.7	626.6	629.7	631.2	636.6	644.3	638.1	639.7
17.5°	609.0	605.2	601.4	599.8	598.3	593.7	599.8	599.1	603.7	604.4	606.7
20°	577.6	574.5	566.9	567.7	569.2	562.3	566.1	566.1	570.7	575.3	580.7
22.5°	547.0	543.9	540.1	541.6	537.0	535.5	535.5	539.3	544.7	548.5	547.7
25°	523.2	517.9	515.6	513.3	511.0	512.5	510.2	514.0	517.9	520.2	517.9
27.5°	496.4	494.1	489.5	487.2	483.4	484.9	486.4	489.5	491.8	491.8	494.1
30°	470.4	467.3	465.8	463.5	463.5	460.4	461.2	464.2	466.5	468.8	471.9
32.5°	445.1	442.8	440.5	440.5	439.0	438.2	437.4	442.0	442.0	446.6	446.6
35°	424.4	420.6	420.6	416.7	418.3	417.5	416.0	419.0	419.8	422.9	422.1
37.5°	401.4	401.4	399.9	396.1	393.0	393.8	397.6	397.6	399.9	399.1	401.4
40°	378.4	376.9	376.9	374.6	373.8	373.1	373.8	374.6	378.4	377.7	378.4
42.5°	355.5	356.2	352.4	352.4	352.4	350.1	350.9	351.6	353.2	354.7	357.0
45°	333.2	331.7	330.9	329.4	327.9	328.6	327.9	330.9	330.2	331.7	334.0
47.5°	309.5	307.2	306.4	303.4	303.4	304.9	304.1	306.4	307.2	309.5	308.0
50°	286.5	283.4	281.1	281.9	277.3	278.8	278.8	281.1	283.4	284.2	285.7
52.5°	259.7	258.9	258.2	254.3	253.6	252.8	253.6	254.3	257.4	259.7	260.5
55°	233.6	232.9	228.3	226.8	224.5	224.5	226.0	226.8	232.1	232.9	235.9
57.5°	209.9	207.6	202.2	201.5	201.5	201.5	199.2	202.2	203.8	207.6	207.6
60°	183.9	183.9	179.3	179.3	180.0	179.3	179.3	180.0	180.0	183.1	184.6
62.5°	163.2	162.4	162.4	160.9	160.1	160.9	160.1	160.1	160.9	163.2	165.5
65°	144.8	144.0	143.3	142.5	141.0	141.0	141.7	143.3	143.3	144.8	145.6
67.5°	127.2	127.2	125.6	125.6	124.9	124.1	124.9	124.1	127.2	127.2	127.9
70°	109.5	108.8	106.5	105.7	103.4	104.2	104.2	106.5	107.2	108.8	110.3
72.5°	88.1	88.1	86.6	85.0	85.8	84.3	84.3	85.0	85.0	87.3	88.1
75°	72.8	71.2	70.5	71.2	70.5	72.0	70.5	70.5	72.0	72.0	72.0
77.5°	59.8	59.8	59.0	59.0	59.8	59.0	59.8	59.8	59.8	59.0	59.8
80°	49.0	48.3	48.3	48.3	47.5	47.5	47.5	47.5	47.5	47.5	47.5
82.5°	36.8	36.8	36.0	36.8	36.8	36.0	36.8	36.0	36.0	36.8	36.8
85°	24.5	26.0	24.5	24.5	25.3	25.3	26.0	25.3	26.0	24.5	25.3
87.5°	13.0	13.8	13.8	13.0	13.0	13.8	13.8	13.8	14.6	13.0	13.8
90°	16.1	16.2	16.5	16.7	17.0	17.2	17.0	16.7	16.5	16.2	16.1
92.5°	25.8	25.7	25.4	25.2	24.9	24.7	24.9	25.2	25.4	25.7	25.8
95°	44.8	44.8	44.8	44.8	44.8	44.8	44.8	44.8	44.8	44.8	44.8
97.5°	64.9	64.8	64.7	64.6	64.4	64.3	64.4	64.6	64.7	64.8	64.9
100°	86.1	86.2	86.5	86.7	87.0	87.2	87.0	86.7	86.5	86.2	86.1
102.5°	111.3	111.2	111.1	111.0	110.9	110.8	110.9	111.0	111.1	111.2	111.3
105°	135.5	135.6	135.9	136.1	136.4	136.6	136.4	136.1	135.9	135.6	135.5
107.5°	163.6	163.5	163.4	163.3	163.1	163.0	163.1	163.3	163.4	163.5	163.6
110°	191.1	191.0	190.7	190.5	190.2	190.0	190.2	190.5	190.7	191.0	191.1

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	218.7	218.7	218.7	218.7	218.7	218.7	218.7	218.7	218.7	218.7	218.7
115°	245.1	245.0	244.9	244.8	244.6	244.5	244.6	244.8	244.9	245.0	245.1
117.5°	272.6	272.4	272.0	271.7	271.3	270.9	271.3	271.7	272.0	272.4	272.6
120°	300.2	300.1	299.8	299.5	299.3	299.0	299.3	299.5	299.8	300.1	300.2
122.5°	327.7	327.5	327.1	326.8	326.4	326.0	326.4	326.8	327.1	327.5	327.7
125°	355.3	355.0	354.5	354.0	353.5	353.0	353.5	354.0	354.5	355.0	355.3
127.5°	382.2	382.0	381.5	381.0	380.5	380.0	380.5	381.0	381.5	382.0	382.2
130°	410.4	410.0	409.1	408.2	407.3	406.4	407.3	408.2	409.1	410.0	410.4
132.5°	436.8	436.5	435.8	435.2	434.5	433.9	434.5	435.2	435.8	436.5	436.8
135°	463.7	463.6	463.3	463.1	462.8	462.6	462.8	463.1	463.3	463.6	463.7
137.5°	489.6	489.4	489.0	488.7	488.3	487.9	488.3	488.7	489.0	489.4	489.6
140°	516.6	516.1	515.2	514.3	513.4	512.5	513.4	514.3	515.2	516.1	516.6
142.5°	540.7	540.4	539.7	539.1	538.4	537.8	538.4	539.1	539.7	540.4	540.7
145°	564.2	563.9	563.4	562.9	562.4	561.9	562.4	562.9	563.4	563.9	564.2
147.5°	587.1	586.7	586.0	585.2	584.5	583.7	584.5	585.2	586.0	586.7	587.1
150°	607.8	607.4	606.7	605.9	605.2	604.4	605.2	605.9	606.7	607.4	607.8
152.5°	627.3	627.0	626.4	625.7	625.1	624.5	625.1	625.7	626.4	627.0	627.3
155°	646.3	645.8	644.9	644.0	643.1	642.2	643.1	644.0	644.9	645.8	646.3
157.5°	662.3	661.9	661.2	660.4	659.7	658.9	659.7	660.4	661.2	661.9	662.3
160°	677.3	677.0	676.5	676.0	675.5	675.0	675.5	676.0	676.5	677.0	677.3
162.5°	691.0	690.6	689.7	688.8	687.9	687.0	687.9	688.8	689.7	690.6	691.0
165°	702.5	702.1	701.2	700.3	699.4	698.5	699.4	700.3	701.2	702.1	702.5
167.5°	712.3	711.9	711.1	710.4	709.6	708.8	709.6	710.4	711.1	711.9	712.3
170°	720.3	719.9	719.0	718.1	717.2	716.3	717.2	718.1	719.0	719.9	720.3
172.5°	726.0	725.6	724.7	723.8	722.9	722.0	722.9	723.8	724.7	725.6	726.0
175°	730.1	729.6	728.7	727.8	726.9	726.0	726.9	727.8	728.7	729.6	730.1
177.5°	732.4	731.9	731.0	730.1	729.2	728.3	729.2	730.1	731.0	731.9	732.4
180°	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8
2.5°	846.5	849.6	846.5	840.4	846.5	850.3	854.2	860.3	863.4	863.4	867.9
5°	798.2	804.4	802.1	800.5	806.7	810.5	816.6	824.3	832.7	838.1	844.2
7.5°	755.3	759.2	763.0	763.0	769.1	777.6	786.7	795.9	806.7	814.3	818.9
10°	717.8	720.9	723.2	726.2	735.4	744.6	756.9	768.4	777.6	786.0	793.6
12.5°	681.8	686.4	691.8	694.1	700.9	712.4	723.9	737.7	752.3	760.7	768.4
15°	647.3	649.6	655.7	662.6	668.8	681.0	695.6	710.1	722.4	735.4	742.3
17.5°	612.1	612.8	628.9	625.1	645.0	656.5	664.2	678.0	697.9	708.6	719.3
20°	577.6	585.3	592.2	596.0	606.7	619.7	642.0	652.7	668.8	678.7	687.9
22.5°	550.8	562.3	562.3	571.5	576.8	589.1	605.2	625.9	643.5	650.4	663.4
25°	527.0	532.4	541.6	544.7	554.6	565.4	576.1	598.3	617.4	626.6	635.8
27.5°	496.4	503.3	515.6	515.6	528.6	540.1	553.1	567.7	586.8	599.8	609.8
30°	472.7	479.6	484.9	493.3	498.7	509.4	532.4	543.1	560.0	571.5	583.7
32.5°	450.4	455.8	460.4	469.6	475.7	488.0	500.2	519.4	533.9	544.7	557.7
35°	425.9	431.3	437.4	444.3	453.5	465.0	476.5	492.6	507.1	517.1	527.8
37.5°	402.9	406.8	416.0	420.6	428.2	439.0	453.5	470.4	483.4	491.0	501.8
40°	380.7	383.8	390.7	399.1	404.5	412.9	428.2	442.8	458.9	468.1	476.5
42.5°	357.0	360.8	366.9	375.4	383.8	393.0	401.4	418.3	432.8	440.5	449.7
45°	336.3	338.6	343.2	351.6	360.0	366.9	380.0	395.3	409.1	415.2	425.2
47.5°	311.8	314.1	321.0	324.8	334.0	343.2	356.2	371.5	383.8	389.9	399.1
50°	286.5	288.8	293.4	301.8	308.0	317.9	329.4	342.4	357.8	366.2	371.5
52.5°	262.0	266.6	270.4	277.3	285.0	294.9	305.7	317.9	330.9	339.4	345.5
55°	237.5	241.3	245.9	249.7	258.9	268.1	280.4	291.9	303.4	311.0	317.9
57.5°	209.9	215.3	219.9	227.5	234.4	242.1	255.9	265.1	278.8	284.2	290.3
60°	186.2	191.5	195.3	201.5	207.6	217.6	226.8	238.2	249.7	256.6	264.3
62.5°	166.2	168.5	170.8	177.0	183.1	192.3	201.5	213.0	225.2	229.1	235.2
65°	146.3	148.6	152.4	157.8	162.4	167.8	177.7	186.9	198.4	204.5	206.8
67.5°	129.5	131.8	132.5	136.4	140.2	146.3	151.7	160.9	171.6	175.4	180.0
70°	110.3	114.1	114.9	118.0	119.5	123.3	129.5	136.4	144.8	151.7	155.5
72.5°	88.1	93.5	95.0	99.6	101.9	105.7	110.3	115.7	121.0	124.1	127.2
75°	72.0	73.5	74.3	78.1	82.0	87.3	89.6	92.7	97.3	101.1	104.2
77.5°	59.8	60.5	61.3	61.3	62.1	65.1	69.7	73.5	76.6	78.1	80.4
80°	48.3	47.5	47.5	48.3	48.3	48.3	49.8	55.2	56.7	60.5	59.8
82.5°	37.5	36.0	36.8	36.0	36.0	36.0	36.0	36.8	36.8	39.1	40.6
85°	24.5	25.3	24.5	24.5	23.7	24.5	23.7	23.7	23.0	23.0	22.2
87.5°	13.0	13.8	13.0	13.0	12.3	13.0	12.3	12.3	11.5	11.5	10.0
90°	15.8	15.3	14.8	14.3	13.8	12.1	10.5	8.8	7.1	6.3	5.7
92.5°	25.6	25.2	24.9	24.5	24.1	23.3	22.6	21.8	21.1	20.7	20.3
95°	44.5	44.0	43.5	43.0	42.5	41.5	40.5	39.4	38.4	37.9	37.5
97.5°	64.6	63.9	63.3	62.6	62.0	61.2	60.4	59.7	58.9	58.5	58.2
100°	85.9	85.5	85.2	84.8	84.4	83.8	83.1	82.5	81.8	81.5	81.1
102.5°	111.1	110.7	110.4	110.0	109.6	108.7	107.8	106.9	106.0	105.6	105.4
105°	135.5	135.5	135.5	135.5	135.5	134.3	133.2	132.0	130.9	130.3	130.2
107.5°	163.4	163.0	162.7	162.3	161.9	161.4	160.9	160.4	159.9	159.6	159.5
110°	190.8	190.3	189.8	189.3	188.8	188.6	188.3	188.1	187.8	187.7	187.6

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	218.4	217.7	217.1	216.4	215.8	215.8	215.8	215.8	215.8	215.8	215.7
115°	245.0	244.9	244.8	244.6	244.5	244.7	245.0	245.2	245.5	245.6	245.4
117.5°	272.6	272.6	272.6	272.6	272.6	272.9	273.1	273.4	273.7	273.8	273.7
120°	300.3	300.4	300.5	300.6	300.7	301.3	302.0	302.6	303.3	303.6	303.2
122.5°	327.9	328.3	328.6	329.0	329.4	329.7	329.9	330.2	330.5	330.6	330.3
125°	355.6	356.1	356.6	357.1	357.6	357.8	358.1	358.3	358.6	358.7	358.5
127.5°	382.6	383.4	384.1	384.9	385.7	385.9	386.2	386.4	386.7	386.8	386.4
130°	410.7	411.2	411.7	412.2	412.7	413.1	413.5	413.8	414.2	414.4	413.9
132.5°	437.1	437.7	438.4	439.0	439.6	439.9	440.1	440.4	440.7	440.8	440.3
135°	464.0	464.5	465.0	465.5	466.0	466.1	466.3	466.4	466.5	466.6	466.2
137.5°	489.9	490.5	491.2	491.8	492.4	492.0	491.6	491.3	490.9	490.7	490.4
140°	516.7	516.8	516.9	517.0	517.1	517.0	516.9	516.8	516.7	516.6	516.3
142.5°	540.8	540.9	541.0	541.1	541.2	541.0	540.7	540.5	540.2	540.1	539.8
145°	564.3	564.4	564.5	564.7	564.8	564.4	564.0	563.6	563.2	563.0	562.9
147.5°	587.1	587.1	587.1	587.1	587.1	586.7	586.3	586.0	585.6	585.4	585.1
150°	607.8	607.8	607.8	607.8	607.8	607.6	607.3	607.1	606.8	606.7	606.6
152.5°	627.2	626.9	626.7	626.4	626.2	626.1	625.9	625.8	625.7	625.6	625.4
155°	646.0	645.5	645.0	644.5	644.0	643.9	643.7	643.6	643.5	643.4	643.4
157.5°	662.0	661.5	661.0	660.5	660.0	659.9	659.8	659.7	659.6	659.5	659.6
160°	677.0	676.3	675.7	675.0	674.4	674.4	674.4	674.4	674.4	674.4	674.5
162.5°	690.7	690.1	689.4	688.8	688.2	688.1	687.9	687.8	687.7	687.6	687.8
165°	702.1	701.4	700.6	699.9	699.1	699.1	699.1	699.1	699.1	699.1	699.3
167.5°	711.9	711.1	710.4	709.6	708.8	708.7	708.6	708.5	708.4	708.3	708.5
170°	719.9	719.0	718.1	717.2	716.3	716.3	716.3	716.3	716.3	716.3	716.6
172.5°	725.6	724.9	724.1	723.4	722.6	722.6	722.6	722.6	722.6	722.6	722.9
175°	729.7	728.9	728.2	727.4	726.6	726.6	726.6	726.6	726.6	726.6	726.9
177.5°	732.0	731.2	730.5	729.7	728.9	728.9	728.9	728.9	728.9	728.9	729.2
180°	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6	730.6

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	894.8	894.8	894.8	894.8
2.5°	871.8	877.1	887.9	897.1
5°	853.4	861.8	877.9	894.0
7.5°	831.2	844.2	864.9	887.1
10°	809.7	826.6	851.9	877.9
12.5°	788.3	805.9	832.7	866.4
15°	763.0	781.4	813.6	854.2
17.5°	740.8	765.3	794.4	835.0
20°	717.0	735.4	773.0	815.9
22.5°	687.2	717.8	753.0	798.2
25°	663.4	690.2	725.5	776.8
27.5°	634.3	665.7	708.6	753.8
30°	610.6	636.6	676.4	730.8
32.5°	583.0	613.6	655.0	708.6
35°	558.5	584.5	623.6	678.0
37.5°	529.3	557.7	601.4	649.6
40°	504.1	531.6	573.0	618.2
42.5°	473.4	502.5	543.9	582.2
45°	448.9	475.7	508.7	543.9
47.5°	419.0	447.4	479.6	504.1
50°	392.2	418.3	443.5	464.2
52.5°	363.1	386.9	409.8	425.2
55°	336.3	354.7	373.1	383.8
57.5°	304.9	322.5	337.8	344.0
60°	277.3	291.9	301.8	308.7
62.5°	248.2	258.9	266.6	270.4
65°	219.9	227.5	231.4	235.2
67.5°	190.7	197.6	199.9	204.5
70°	160.1	167.8	169.3	171.6
72.5°	137.1	137.1	140.2	143.3
75°	109.5	111.1	112.6	112.6
77.5°	85.8	85.8	87.3	88.1
80°	62.8	63.6	63.6	62.8
82.5°	42.9	44.4	42.9	42.1
85°	23.7	26.8	25.3	25.3
87.5°	10.0	10.0	11.5	10.0
90°	4.4	3.1	1.9	0.6
92.5°	19.5	18.8	18.0	17.2
95°	36.6	35.7	34.8	33.9
97.5°	57.6	56.9	56.3	55.7
100°	80.4	79.6	78.9	78.1
102.5°	105.0	104.7	104.3	103.9
105°	129.9	129.6	129.4	129.1
107.5°	159.4	159.3	159.1	159.0
110°	187.3	187.0	186.8	186.5

TEST NUMBER: P1012653

CATALOG NUMBER: S123RDIP-B560D585UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	215.6	215.5	215.3	215.2
115°	245.0	244.7	244.3	243.9
117.5°	273.6	273.5	273.3	273.2
120°	302.5	301.7	301.0	300.2
122.5°	329.8	329.3	328.8	328.3
125°	358.1	357.8	357.4	357.0
127.5°	385.7	384.9	384.2	383.4
130°	412.9	411.8	410.8	409.8
132.5°	439.3	438.2	437.2	436.2
135°	465.5	464.7	464.0	463.2
137.5°	489.8	489.1	488.5	487.9
140°	515.6	515.0	514.3	513.7
142.5°	539.1	538.5	537.8	537.2
145°	562.6	562.4	562.1	561.9
147.5°	584.6	584.1	583.6	583.1
150°	606.3	606.0	605.8	605.5
152.5°	625.0	624.7	624.3	623.9
155°	643.4	643.4	643.4	643.4
157.5°	659.7	659.8	659.9	660.0
160°	674.8	675.0	675.3	675.5
162.5°	688.2	688.5	688.9	689.3
165°	699.7	700.0	700.4	700.8
167.5°	709.0	709.5	710.0	710.5
170°	717.1	717.6	718.1	718.6
172.5°	723.4	723.9	724.4	724.9
175°	727.4	727.9	728.4	728.9
177.5°	729.7	730.2	730.7	731.2
180°	730.6	730.6	730.6	730.6

(END OF REPORT)