

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012672

Luminaire Tested: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012672
REPORT IS A COMBINATION OF REPORTS P993481 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D805UB27-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5015.0 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51			44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	45	44			38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38			33
3	81	72	65	60	74	66	60	56	56	51	48	46	43	40	36	34	33			28
4	74	64	57	51	68	59	53	48	50	45	41	41	37	35	33	30	28			25
5	69	57	50	44	63	53	46	41	45	40	36	37	33	30	30	27	25			22
6	63	52	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22			19
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20			17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18			16
9	51	39	32	27	46	36	30	25	31	26	22	26	22	19	21	18	16			14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9510	9510	9510	9510
5°	9518	10953	9542	8126
10°	9434	13222	9475	7098
15°	9336	15006	9336	6258
20°	9145	16186	9196	5551
25°	9004	15378	8987	5066
30°	8841	10655	8823	4590
35°	8645	6841	8606	4232
40°	8401	4831	8359	3876
45°	7977	3865	7965	3528
50°	7454	3234	7430	3122
55°	6867	2665	6811	2647
60°	6289	2203	6227	2251
65°	5613	1763	5649	1908
70°	4989	1225	5124	1543
75°	4230	909	4401	1186
80°	3366	603	3654	889
85°	2401	286	2613	554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 12696 cd/sqm

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	1.7
10°-20°	271.6	5.4
20°-30°	427.8	8.5
30°-40°	444.8	8.9
40°-50°	380.6	7.6
50°-60°	290.1	5.8
60°-70°	185.9	3.7
70°-80°	89.1	1.8
80°-90°	25.5	0.5
90°-100°	202.9	4.0
100°-110°	594.1	11.8
110°-120°	580.2	11.6
120°-130°	462.0	9.2
130°-140°	364.5	7.3
140°-150°	271.9	5.4
150°-160°	189.6	3.8
160°-170°	111.4	2.2
170°-180°	36.2	0.7
0°-30°	786.1	15.7
0°-40°	1231.0	24.5
0°-60°	1901.6	37.9
0°-90°	2202.1	43.9
90°-120°	1377.2	27.5
90°-150°	2475.7	49.4
90°-180°	2813.0	56.1
0°-180°	5015.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	884	884	884	884	884	
5°	883	1049	885	778	883	84
15°	843	1491	843	622	843	237
25°	767	1536	766	506	767	353
35°	669	666	666	412	669	419
45°	537	356	536	324	537	414
55°	379	223	376	222	379	340
65°	232	129	234	139	232	232
75°	111	54	116	71	111	120
85°	25	13	27	25	25	28
90°	2	22	2	22	2	3
95°	26	88	26	88	26	27
105°	88	963	88	963	88	93
115°	155	1171	155	1171	155	154
125°	216	924	216	924	216	192
135°	253	749	253	749	253	195
145°	288	585	288	585	288	181
155°	328	485	328	485	328	151
165°	358	423	358	423	358	101
175°	373	381	373	381	373	35
180°	374	374	374	374	374	

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	885.8	891.8	896.4	899.4	907.0	911.5	915.3	922.1	922.1	923.6	926.6
5°	882.8	895.6	904.7	916.8	932.7	940.2	950.8	959.9	972.8	979.6	986.4
7.5°	876.0	894.1	913.0	931.2	954.6	969.7	980.3	1003.8	1020.4	1040.9	1056.7
10°	866.9	891.8	916.0	944.0	975.8	998.5	1014.4	1045.4	1077.2	1105.9	1130.1
12.5°	855.5	885.8	920.6	954.6	999.2	1021.9	1047.7	1086.2	1131.6	1167.9	1200.5
15°	843.4	878.2	917.6	959.2	1015.1	1046.9	1084.0	1130.9	1181.5	1233.7	1278.4
17.5°	824.5	868.4	912.3	972.8	1038.6	1057.5	1089.3	1153.6	1216.3	1263.2	1317.7
20°	805.6	854.8	910.0	964.5	1035.6	1079.4	1108.9	1177.0	1244.3	1301.1	1353.3
22.5°	788.2	839.6	897.1	966.0	1032.5	1076.4	1113.5	1184.6	1262.5	1326.0	1390.3
25°	767.0	823.0	886.5	951.6	1032.5	1065.8	1106.7	1189.1	1271.6	1344.9	1424.4
27.5°	744.3	801.1	863.8	930.4	1004.5	1053.7	1093.8	1182.3	1282.9	1361.6	1443.3
30°	721.6	779.9	840.4	900.2	983.4	1030.3	1076.4	1174.0	1289.0	1379.0	1441.8
32.5°	699.7	748.9	808.6	866.9	949.3	1000.8	1053.0	1165.7	1291.2	1366.9	1397.1
35°	669.4	720.9	769.3	831.3	914.5	965.2	1026.5	1164.9	1281.4	1328.3	1313.2
37.5°	641.5	684.6	730.7	785.9	871.4	937.2	1000.8	1145.2	1248.9	1251.9	1166.4
40°	610.4	646.0	684.6	742.8	835.1	900.2	969.0	1115.0	1189.9	1145.2	994.7
42.5°	574.9	606.7	636.9	693.6	794.3	866.9	941.0	1077.2	1104.4	1001.5	844.9
45°	537.1	562.8	590.8	650.5	751.1	823.0	897.1	1018.9	990.9	845.7	696.7
47.5°	497.7	519.7	546.9	601.4	705.0	778.4	848.7	935.7	864.6	708.8	584.0
50°	458.4	475.8	502.3	558.2	658.1	724.7	789.7	846.4	746.6	608.2	482.6
52.5°	419.8	433.4	460.7	508.3	605.1	668.7	715.6	737.5	636.2	502.3	419.1
55°	379.0	394.1	412.3	460.7	556.7	603.6	634.6	633.9	529.5	425.9	346.4
57.5°	339.6	353.3	369.1	417.6	495.5	527.2	553.7	540.9	441.8	348.7	297.3
60°	304.8	312.4	329.8	370.7	429.7	456.9	472.0	450.1	360.8	294.3	245.8
62.5°	267.0	274.6	289.0	327.5	363.8	378.2	391.1	363.1	298.0	239.8	210.3
65°	232.2	242.1	251.1	282.1	301.8	319.2	317.7	294.3	233.0	195.2	171.0
67.5°	202.0	205.7	213.3	232.2	241.3	254.2	254.9	228.4	187.6	158.9	144.5
70°	169.4	173.2	178.5	187.6	193.6	196.7	195.2	171.7	141.5	124.1	111.2
72.5°	141.5	140.7	144.5	144.5	150.5	149.8	145.2	127.1	107.4	93.0	85.5
75°	111.2	112.0	112.7	111.2	108.9	105.9	102.1	88.5	75.6	68.8	62.0
77.5°	87.0	85.5	86.2	80.9	77.9	74.9	69.6	62.8	52.2	50.7	47.7
80°	62.0	61.3	60.5	58.2	51.4	48.4	44.6	40.8	38.6	37.1	36.3
82.5°	41.6	41.6	40.1	35.6	31.8	29.5	28.7	27.2	25.0	25.0	24.2
85°	25.0	24.2	22.7	18.2	15.9	15.9	15.9	15.9	14.4	14.4	13.6
87.5°	9.8	9.1	6.8	6.8	6.1	6.1	6.1	5.3	5.3	4.5	4.5
90°	1.5	3.0	4.5	6.8	8.3	9.0	9.8	12.1	14.4	16.7	18.9
92.5°	11.4	16.7	24.2	31.0	38.6	45.4	52.2	76.5	116.6	155.9	140.8
95°	25.7	28.0	36.3	49.2	68.9	83.6	98.4	162.8	275.5	399.7	448.9
97.5°	40.9	41.6	48.4	59.8	79.5	95.8	112.0	175.6	306.6	515.5	690.4
100°	56.0	56.8	62.1	72.7	90.8	105.6	120.4	173.4	285.4	484.5	716.9
102.5°	71.9	73.4	78.0	87.8	103.7	117.0	130.2	176.4	267.2	439.1	667.7
105°	87.8	90.1	94.6	103.7	118.1	129.8	141.6	182.4	260.4	403.5	608.6
107.5°	104.5	106.7	111.3	120.4	134.0	145.0	155.9	192.3	258.9	377.7	556.4
110°	122.6	124.9	128.7	137.0	149.9	160.5	171.1	205.1	262.7	364.1	513.2

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	139.3	141.6	145.3	153.7	166.5	176.8	187.0	218.0	270.2	356.5	484.5
115°	155.2	158.2	162.8	170.3	183.2	193.4	203.6	232.4	278.6	355.8	465.6
117.5°	171.1	174.9	178.7	185.5	199.8	209.3	218.8	247.5	289.2	356.5	452.7
120°	187.7	190.0	193.8	201.4	215.7	225.2	234.7	261.9	301.3	359.6	444.4
122.5°	202.1	204.4	208.2	216.5	230.1	240.4	250.6	277.1	312.6	364.9	439.1
125°	215.7	217.3	221.8	230.1	244.5	254.7	264.9	291.4	324.8	370.2	434.5
127.5°	226.3	228.6	233.9	242.2	258.1	268.4	278.6	304.3	334.6	376.2	432.2
130°	236.2	238.5	245.3	254.4	270.2	280.4	290.7	315.7	344.4	382.3	430.0
132.5°	243.8	246.8	254.4	265.7	281.6	291.5	301.3	325.5	353.5	386.8	429.2
135°	252.8	255.9	264.2	275.5	291.4	301.6	311.9	335.3	361.1	391.4	428.5
137.5°	261.2	264.2	272.5	284.6	300.5	310.0	319.5	342.2	367.1	394.4	426.9
140°	269.5	273.3	280.8	293.0	308.1	317.6	327.0	349.0	371.7	397.4	426.2
142.5°	278.6	281.6	289.9	300.5	315.7	324.4	333.1	354.3	376.2	399.7	424.7
145°	288.4	290.7	297.5	308.9	321.7	330.4	339.1	358.8	379.3	400.5	423.2
147.5°	298.3	299.8	306.6	316.4	329.3	336.8	344.4	362.6	381.5	400.5	420.9
150°	308.1	308.9	314.9	324.8	335.3	342.2	349.0	366.4	382.3	400.5	417.9
152.5°	317.9	317.9	324.0	332.3	341.4	347.8	354.3	368.7	383.8	398.2	414.1
155°	327.8	327.8	332.3	339.9	348.2	353.5	358.8	371.7	383.8	396.7	409.5
157.5°	335.3	336.1	339.9	346.7	354.3	358.5	362.6	373.2	384.6	394.4	405.7
160°	344.4	344.4	347.5	353.5	358.8	362.6	366.4	375.5	384.6	392.9	401.2
162.5°	351.2	351.2	353.5	358.1	362.6	365.6	368.7	376.2	383.8	389.9	396.7
165°	358.1	357.3	358.8	362.6	365.6	368.2	370.9	377.0	382.3	386.8	392.1
167.5°	363.4	362.6	363.4	366.4	368.7	370.5	372.4	377.0	381.5	383.8	387.6
170°	367.9	366.4	367.1	369.4	370.9	371.6	372.4	376.2	379.3	380.8	383.0
172.5°	370.9	370.2	370.2	371.7	372.4	372.8	373.2	376.2	378.5	378.5	379.3
175°	373.2	372.4	371.7	373.2	373.2	373.6	374.0	375.5	377.0	376.2	376.2
177.5°	374.7	374.0	373.2	374.0	374.0	374.0	374.0	374.7	376.2	374.7	374.0
180°	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	932.7	932.7	939.5	946.3	942.5	944.8	953.1	950.1	956.1	955.4	957.6
5°	1003.0	1011.4	1018.2	1032.5	1034.8	1032.5	1046.9	1050.7	1057.5	1049.2	1053.0
7.5°	1082.5	1099.9	1116.5	1137.7	1144.5	1146.0	1153.6	1164.2	1173.2	1156.6	1164.9
10°	1159.6	1186.1	1220.1	1239.0	1255.7	1261.7	1267.8	1274.6	1285.2	1295.0	1287.5
12.5°	1242.8	1281.4	1313.9	1348.0	1368.4	1366.1	1383.5	1388.1	1396.4	1398.6	1401.7
15°	1310.9	1365.4	1385.8	1436.5	1441.0	1456.1	1475.8	1493.2	1495.5	1490.9	1490.9
17.5°	1376.0	1422.9	1459.2	1500.0	1508.3	1521.2	1546.2	1554.5	1557.5	1556.7	1556.7
20°	1428.9	1459.9	1521.2	1555.2	1568.8	1585.5	1602.9	1613.5	1615.7	1618.8	1614.2
22.5°	1463.7	1510.6	1560.5	1588.5	1599.9	1605.9	1617.3	1620.3	1616.5	1617.3	1618.0
25°	1490.9	1537.1	1567.3	1574.9	1574.1	1566.6	1558.3	1543.9	1542.4	1536.3	1524.2
27.5°	1498.5	1515.9	1512.1	1481.1	1450.1	1447.1	1397.1	1369.9	1338.9	1343.4	1326.0
30°	1457.6	1435.0	1381.2	1302.6	1270.1	1217.1	1161.1	1102.9	1080.2	1055.2	1101.4
32.5°	1357.8	1276.9	1181.5	1079.4	1025.0	978.1	918.3	876.0	851.7	831.3	870.7
35°	1207.3	1080.9	954.6	857.8	813.2	770.8	714.8	693.6	663.4	666.4	670.2
37.5°	1013.6	874.4	779.1	683.8	654.3	636.9	596.1	563.5	553.0	549.9	549.9
40°	832.1	717.9	633.1	558.2	535.6	521.2	488.7	473.5	462.2	459.2	462.9
42.5°	688.4	590.8	525.0	475.0	459.2	441.0	427.4	408.5	406.2	400.9	407.7
45°	577.9	493.2	444.0	407.7	394.1	387.3	372.2	360.8	356.3	355.5	360.8
47.5°	490.2	424.4	381.2	358.5	348.0	341.2	328.3	323.8	319.2	320.7	318.5
50°	411.5	362.3	334.3	313.9	307.1	300.3	292.0	287.4	285.2	285.2	284.4
52.5°	353.3	312.4	294.3	275.3	272.3	268.5	259.5	256.4	252.6	251.9	254.9
55°	302.6	274.6	256.4	245.1	242.1	234.5	230.7	226.9	224.7	223.1	223.9
57.5°	258.7	237.5	225.4	215.6	210.3	207.3	200.5	199.7	198.2	198.2	197.4
60°	222.4	207.3	192.9	186.8	183.1	179.3	178.5	174.0	171.7	173.2	172.5
62.5°	188.4	176.2	167.9	161.1	158.9	155.8	153.6	152.0	149.8	150.5	150.5
65°	157.3	147.5	141.5	135.4	134.6	131.6	130.9	129.4	129.4	128.6	130.1
67.5°	129.4	122.5	117.2	113.5	111.2	112.0	108.9	106.7	106.7	105.9	108.2
70°	102.9	99.1	93.8	89.3	86.2	86.2	82.5	81.7	81.7	81.7	80.9
72.5°	79.4	72.6	70.3	68.8	68.8	68.8	67.3	67.3	66.6	67.3	66.6
75°	59.0	58.2	56.7	56.0	56.0	55.2	54.5	54.5	54.5	54.5	54.5
77.5°	46.1	46.1	44.6	43.9	43.9	43.9	43.1	43.1	42.4	42.4	42.4
80°	34.0	34.0	32.5	32.5	32.5	31.8	31.8	31.8	32.5	31.8	31.8
82.5°	23.4	23.4	22.7	23.4	22.7	21.9	21.9	21.9	21.2	21.9	21.9
85°	13.6	13.6	12.9	12.1	12.9	12.9	12.1	12.9	12.1	12.9	12.1
87.5°	5.3	4.5	4.5	4.5	3.8	4.5	3.8	3.8	4.5	3.8	4.5
90°	18.2	18.9	19.7	20.4	21.2	22.0	21.2	22.0	22.7	22.0	22.7
92.5°	105.2	74.9	58.3	50.7	48.0	45.4	43.9	40.9	41.6	40.1	41.6
95°	364.1	272.5	184.7	144.6	131.0	117.3	103.0	96.1	90.8	87.8	90.8
97.5°	713.8	626.0	472.4	372.4	329.2	286.1	235.4	206.7	188.5	180.2	188.5
100°	866.0	892.5	831.2	742.6	688.8	635.1	558.7	503.4	473.9	474.6	473.9
102.5°	873.6	981.1	993.9	951.5	922.4	893.3	838.0	797.1	773.6	751.7	773.6
105°	825.9	984.1	1059.8	1074.2	1064.4	1054.5	1019.7	990.9	966.7	962.9	966.7
107.5°	757.8	938.7	1057.5	1116.6	1126.8	1137.0	1132.5	1118.8	1109.0	1100.7	1109.0
110°	694.2	867.5	1006.8	1102.2	1128.7	1155.2	1176.4	1182.4	1180.9	1179.4	1180.9

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	638.9	797.1	940.2	1050.0	1086.0	1121.9	1165.0	1187.0	1194.5	1195.3	1194.5
115°	596.5	736.6	868.3	979.6	1020.8	1062.1	1118.8	1152.1	1167.3	1171.1	1167.3
117.5°	568.5	689.6	806.2	908.4	951.2	993.9	1053.0	1090.1	1112.8	1118.1	1112.8
120°	547.3	654.0	756.2	847.1	885.3	923.5	983.3	1025.7	1043.9	1048.4	1043.9
122.5°	529.9	626.0	716.1	798.6	833.4	868.3	919.7	956.8	977.3	983.3	977.3
125°	515.5	601.8	684.3	757.0	787.3	817.6	866.0	899.3	918.2	923.5	918.2
127.5°	501.9	579.9	654.8	721.4	749.4	777.4	821.3	850.1	867.5	872.1	867.5
130°	491.3	559.4	627.5	688.9	714.6	740.3	780.5	807.7	823.6	829.7	823.6
132.5°	481.4	540.5	601.8	657.8	682.0	706.3	743.4	770.6	784.2	788.0	784.2
135°	473.1	523.8	577.6	626.8	648.3	669.9	707.0	729.7	743.4	748.7	743.4
137.5°	465.6	507.9	553.4	597.3	616.6	635.9	667.7	691.1	702.5	707.0	702.5
140°	458.7	494.3	532.9	569.3	585.6	601.8	630.6	651.8	663.9	663.1	663.9
142.5°	452.7	481.4	513.2	543.5	557.2	570.8	594.2	612.4	623.0	622.2	623.0
145°	447.4	471.6	496.6	520.8	531.8	542.8	561.7	577.6	583.6	585.2	583.6
147.5°	442.1	463.3	483.7	504.2	512.2	520.1	535.2	546.6	552.6	553.4	552.6
150°	436.8	454.2	471.6	487.5	494.7	501.9	513.2	521.6	526.1	526.1	526.1
152.5°	430.7	445.9	460.3	473.9	479.6	485.2	493.6	501.1	503.4	503.4	503.4
155°	424.7	437.5	449.7	461.0	465.6	470.1	476.9	483.0	484.5	485.2	484.5
157.5°	417.9	428.5	439.1	448.1	451.9	455.7	461.8	466.3	467.8	467.8	467.8
160°	411.0	420.9	429.2	436.8	439.4	442.1	447.4	451.9	451.9	451.2	451.9
162.5°	404.2	411.8	418.6	425.4	427.7	430.0	433.0	436.8	436.8	436.0	436.8
165°	398.2	404.2	408.8	414.1	416.0	417.9	420.9	423.9	423.2	423.2	423.2
167.5°	392.1	397.4	401.2	404.2	405.8	407.3	408.8	411.0	410.3	410.3	410.3
170°	386.8	390.6	392.9	395.9	396.6	397.4	398.2	399.7	398.9	398.9	398.9
172.5°	381.5	384.6	386.1	388.3	388.7	389.1	389.1	390.6	389.1	388.3	389.1
175°	377.7	379.3	380.0	381.5	381.5	381.5	381.5	382.3	381.5	380.8	381.5
177.5°	374.7	375.5	376.2	377.0	377.0	377.0	376.2	377.0	375.5	375.5	375.5
180°	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	953.9	949.3	946.3	944.0	941.8	948.6	939.5	929.7	922.8	918.3	916.8
5°	1053.7	1043.9	1035.6	1028.7	1030.3	1030.3	1014.4	997.0	981.9	973.5	964.5
7.5°	1169.4	1158.9	1142.2	1138.4	1135.4	1116.5	1100.6	1068.8	1049.9	1031.0	1014.4
10°	1284.4	1270.8	1254.9	1249.6	1242.1	1218.6	1194.4	1153.6	1130.1	1095.3	1073.4
12.5°	1391.8	1375.2	1359.3	1355.5	1344.2	1323.8	1282.2	1239.8	1199.7	1162.6	1124.1
15°	1481.9	1477.3	1453.1	1438.0	1413.0	1385.0	1376.0	1318.5	1267.8	1229.2	1159.6
17.5°	1557.5	1536.3	1513.6	1503.8	1494.0	1461.4	1428.9	1369.9	1315.4	1258.7	1214.1
20°	1618.0	1594.6	1578.7	1564.3	1559.8	1522.7	1471.3	1419.1	1359.3	1295.8	1237.5
22.5°	1621.0	1618.0	1607.4	1599.1	1590.0	1565.8	1525.0	1459.9	1396.4	1326.8	1250.4
25°	1558.3	1553.7	1584.0	1576.4	1582.5	1573.4	1551.4	1497.0	1422.9	1341.2	1264.0
27.5°	1369.1	1415.3	1462.9	1479.6	1490.9	1523.5	1534.0	1503.8	1444.0	1357.0	1270.8
30°	1112.0	1173.2	1250.4	1292.0	1323.8	1384.3	1462.9	1472.8	1444.8	1375.2	1269.3
32.5°	872.9	928.9	990.9	1040.1	1082.5	1206.5	1312.4	1388.8	1402.4	1366.1	1273.1
35°	703.5	727.7	786.7	833.6	891.1	997.0	1121.8	1245.1	1328.3	1332.8	1261.7
37.5°	580.2	593.0	644.5	671.0	705.0	798.0	914.5	1075.6	1205.0	1266.3	1230.0
40°	480.3	509.8	539.3	554.5	578.7	643.0	754.9	881.2	1041.6	1155.1	1180.8
42.5°	416.8	429.7	448.6	469.7	484.9	540.9	615.7	731.5	876.0	1034.0	1105.1
45°	367.6	372.2	391.8	405.4	421.3	460.7	513.6	610.4	737.5	893.3	1014.4
47.5°	326.8	335.9	346.4	354.8	365.4	395.6	441.0	511.3	623.3	762.5	892.6
50°	290.5	295.8	309.4	313.2	320.7	341.9	376.7	430.4	522.7	633.9	768.5
52.5°	256.4	266.3	271.6	276.9	283.7	301.1	323.8	367.6	437.2	541.6	655.8
55°	230.0	233.0	240.5	245.1	250.4	262.5	282.1	314.7	369.1	452.3	560.5
57.5°	204.2	204.2	211.8	215.6	220.9	230.0	247.4	272.3	311.7	373.7	472.8
60°	177.0	177.8	183.8	188.4	189.9	198.9	213.3	233.0	263.2	308.6	389.6
62.5°	152.8	156.6	159.6	161.1	166.4	171.7	183.8	197.4	218.6	258.7	316.2
65°	132.4	133.1	135.4	136.9	139.2	145.2	154.3	163.4	181.5	211.0	257.9
67.5°	108.9	112.0	115.0	115.0	117.2	120.3	129.4	136.9	150.5	167.9	199.7
70°	81.7	83.2	87.7	90.0	93.0	98.3	102.9	107.4	118.0	130.9	155.1
72.5°	68.1	68.1	69.6	70.3	70.3	74.1	80.9	85.5	90.8	99.8	116.5
75°	54.5	54.5	56.7	56.0	57.5	59.0	59.8	62.8	65.8	72.6	82.5
77.5°	43.1	43.9	43.9	44.6	44.6	45.4	46.1	47.7	49.2	53.0	57.5
80°	31.8	32.5	32.5	33.3	33.3	34.0	34.8	35.6	37.1	38.6	40.8
82.5°	21.9	22.7	22.7	23.4	22.7	23.4	24.2	24.2	25.0	26.5	27.2
85°	12.9	12.9	13.6	12.9	12.9	12.9	13.6	13.6	14.4	16.6	16.6
87.5°	3.8	4.5	3.8	4.5	4.5	4.5	4.5	5.3	5.3	6.1	6.8
90°	22.0	21.2	22.0	21.2	20.4	19.7	18.9	18.2	18.9	16.7	14.4
92.5°	40.9	43.9	45.4	48.0	50.7	58.3	74.9	105.2	140.8	155.9	116.6
95°	96.1	103.0	117.3	131.0	144.6	184.7	272.5	364.1	448.9	399.7	275.5
97.5°	206.7	235.4	286.1	329.2	372.4	472.4	626.0	713.8	690.4	515.5	306.6
100°	503.4	558.7	635.1	688.8	742.6	831.2	892.5	866.0	716.9	484.5	285.4
102.5°	797.1	838.0	893.3	922.4	951.5	993.9	981.1	873.6	667.7	439.1	267.2
105°	990.9	1019.7	1054.5	1064.4	1074.2	1059.8	984.1	825.9	608.6	403.5	260.4
107.5°	1118.8	1132.5	1137.0	1126.8	1116.6	1057.5	938.7	757.8	556.4	377.7	258.9
110°	1182.4	1176.4	1155.2	1128.7	1102.2	1006.8	867.5	694.2	513.2	364.1	262.7

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1187.0	1165.0	1121.9	1086.0	1050.0	940.2	797.1	638.9	484.5	356.5	270.2
115°	1152.1	1118.8	1062.1	1020.8	979.6	868.3	736.6	596.5	465.6	355.8	278.6
117.5°	1090.1	1053.0	993.9	951.2	908.4	806.2	689.6	568.5	452.7	356.5	289.2
120°	1025.7	983.3	923.5	885.3	847.1	756.2	654.0	547.3	444.4	359.6	301.3
122.5°	956.8	919.7	868.3	833.4	798.6	716.1	626.0	529.9	439.1	364.9	312.6
125°	899.3	866.0	817.6	787.3	757.0	684.3	601.8	515.5	434.5	370.2	324.8
127.5°	850.1	821.3	777.4	749.4	721.4	654.8	579.9	501.9	432.2	376.2	334.6
130°	807.7	780.5	740.3	714.6	688.9	627.5	559.4	491.3	430.0	382.3	344.4
132.5°	770.6	743.4	706.3	682.0	657.8	601.8	540.5	481.4	429.2	386.8	353.5
135°	729.7	707.0	669.9	648.3	626.8	577.6	523.8	473.1	428.5	391.4	361.1
137.5°	691.1	667.7	635.9	616.6	597.3	553.4	507.9	465.6	426.9	394.4	367.1
140°	651.8	630.6	601.8	585.6	569.3	532.9	494.3	458.7	426.2	397.4	371.7
142.5°	612.4	594.2	570.8	557.2	543.5	513.2	481.4	452.7	424.7	399.7	376.2
145°	577.6	561.7	542.8	531.8	520.8	496.6	471.6	447.4	423.2	400.5	379.3
147.5°	546.6	535.2	520.1	512.2	504.2	483.7	463.3	442.1	420.9	400.5	381.5
150°	521.6	513.2	501.9	494.7	487.5	471.6	454.2	436.8	417.9	400.5	382.3
152.5°	501.1	493.6	485.2	479.6	473.9	460.3	445.9	430.7	414.1	398.2	383.8
155°	483.0	476.9	470.1	465.6	461.0	449.7	437.5	424.7	409.5	396.7	383.8
157.5°	466.3	461.8	455.7	451.9	448.1	439.1	428.5	417.9	405.7	394.4	384.6
160°	451.9	447.4	442.1	439.4	436.8	429.2	420.9	411.0	401.2	392.9	384.6
162.5°	436.8	433.0	430.0	427.7	425.4	418.6	411.8	404.2	396.7	389.9	383.8
165°	423.9	420.9	417.9	416.0	414.1	408.8	404.2	398.2	392.1	386.8	382.3
167.5°	411.0	408.8	407.3	405.8	404.2	401.2	397.4	392.1	387.6	383.8	381.5
170°	399.7	398.2	397.4	396.6	395.9	392.9	390.6	386.8	383.0	380.8	379.3
172.5°	390.6	389.1	389.1	388.7	388.3	386.1	384.6	381.5	379.3	378.5	378.5
175°	382.3	381.5	381.5	381.5	381.5	380.0	379.3	377.7	376.2	376.2	377.0
177.5°	377.0	376.2	377.0	377.0	377.0	376.2	375.5	374.7	374.0	374.7	376.2
180°	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	914.5	910.7	907.0	907.0	898.6	891.1	887.3	888.8	884.3	878.2	872.2
5°	954.6	939.5	936.5	928.1	916.8	900.9	892.6	885.0	876.0	863.8	852.5
7.5°	991.7	972.0	961.4	953.1	931.2	909.2	891.1	879.0	863.1	844.9	831.3
10°	1040.1	1003.8	992.4	973.5	942.5	911.5	890.3	870.7	848.7	827.5	809.4
12.5°	1078.7	1037.1	1015.9	997.0	956.9	917.6	882.0	857.8	831.3	807.9	784.4
15°	1122.5	1075.6	1038.6	1015.9	965.2	917.6	877.5	843.4	813.9	785.2	764.8
17.5°	1143.7	1084.7	1068.1	1035.6	962.2	914.5	865.4	829.1	793.5	760.2	736.0
20°	1177.0	1108.2	1066.6	1044.6	979.6	909.2	851.7	810.1	773.1	737.5	711.8
22.5°	1179.3	1104.4	1077.2	1035.6	955.4	893.3	839.6	789.0	745.8	712.6	686.1
25°	1174.0	1097.6	1059.8	1026.5	959.9	884.3	815.4	765.5	723.2	684.6	653.6
27.5°	1171.7	1077.9	1042.4	1009.1	934.2	857.8	801.1	744.3	695.9	661.9	630.1
30°	1168.7	1056.7	1013.6	975.0	906.2	837.4	769.3	720.1	674.0	630.9	599.1
32.5°	1149.0	1028.0	984.1	943.3	869.1	800.3	746.6	694.4	644.5	604.4	575.6
35°	1143.0	1001.5	944.0	900.2	827.5	766.3	709.5	666.4	619.5	579.4	545.4
37.5°	1125.6	974.3	912.3	856.3	780.6	722.4	680.8	637.7	592.3	549.2	521.9
40°	1095.3	942.5	872.2	814.7	736.8	677.8	639.2	607.4	562.8	524.2	490.9
42.5°	1050.7	910.0	834.3	773.8	687.6	632.4	600.6	570.4	532.5	492.4	465.2
45°	999.2	866.9	796.5	729.2	641.5	587.7	554.5	536.3	501.5	467.5	435.7
47.5°	928.9	822.2	752.7	683.1	593.8	541.6	515.1	497.0	472.8	435.7	410.0
50°	840.4	764.8	698.9	636.9	546.9	497.0	470.5	456.9	436.5	410.0	385.0
52.5°	742.1	698.2	643.7	586.2	499.2	452.3	428.1	417.6	402.4	377.5	356.3
55°	643.0	624.1	587.0	530.3	449.3	410.7	389.6	375.9	364.6	346.4	328.3
57.5°	554.5	545.4	519.7	475.8	407.7	367.6	349.5	340.4	331.3	317.7	299.5
60°	462.9	472.8	446.3	424.4	362.3	327.5	311.7	301.8	297.3	285.2	273.8
62.5°	383.5	392.6	377.5	360.8	316.9	285.9	276.1	267.0	264.0	253.4	242.1
65°	311.7	323.0	311.7	302.6	276.1	250.4	238.3	233.7	230.7	223.9	214.8
67.5°	248.1	259.5	254.2	242.8	234.5	213.3	206.5	202.0	200.5	195.2	187.6
70°	186.8	202.7	204.2	197.4	189.9	180.0	175.5	174.0	170.2	165.7	161.1
72.5°	134.6	152.8	153.6	153.6	149.0	149.0	144.5	142.2	142.2	137.7	132.4
75°	99.1	111.2	112.7	114.2	116.5	118.8	115.7	115.7	115.0	110.4	108.2
77.5°	65.8	76.4	80.2	85.5	88.5	88.5	90.0	91.5	90.0	87.7	86.2
80°	42.4	49.9	54.5	57.5	62.0	64.3	66.6	67.3	65.8	65.1	62.8
82.5°	28.0	30.3	32.5	36.3	41.6	45.4	45.4	44.6	46.1	45.4	44.6
85°	15.9	17.4	18.2	18.9	21.9	25.7	26.5	27.2	28.7	27.2	25.7
87.5°	6.1	6.8	6.8	6.8	8.3	9.1	11.3	14.4	13.6	12.1	12.1
90°	12.1	9.8	9.0	8.3	6.8	4.5	3.0	1.5	3.0	4.5	6.8
92.5°	76.5	52.2	45.4	38.6	31.0	24.2	16.7	11.4	16.7	24.2	31.0
95°	162.8	98.4	83.6	68.9	49.2	36.3	28.0	25.7	28.0	36.3	49.2
97.5°	175.6	112.0	95.8	79.5	59.8	48.4	41.6	40.9	41.6	48.4	59.8
100°	173.4	120.4	105.6	90.8	72.7	62.1	56.8	56.0	56.8	62.1	72.7
102.5°	176.4	130.2	117.0	103.7	87.8	78.0	73.4	71.9	73.4	78.0	87.8
105°	182.4	141.6	129.8	118.1	103.7	94.6	90.1	87.8	90.1	94.6	103.7
107.5°	192.3	155.9	145.0	134.0	120.4	111.3	106.7	104.5	106.7	111.3	120.4
110°	205.1	171.1	160.5	149.9	137.0	128.7	124.9	122.6	124.9	128.7	137.0

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	218.0	187.0	176.8	166.5	153.7	145.3	141.6	139.3	141.6	145.3	153.7
115°	232.4	203.6	193.4	183.2	170.3	162.8	158.2	155.2	158.2	162.8	170.3
117.5°	247.5	218.8	209.3	199.8	185.5	178.7	174.9	171.1	174.9	178.7	185.5
120°	261.9	234.7	225.2	215.7	201.4	193.8	190.0	187.7	190.0	193.8	201.4
122.5°	277.1	250.6	240.4	230.1	216.5	208.2	204.4	202.1	204.4	208.2	216.5
125°	291.4	264.9	254.7	244.5	230.1	221.8	217.3	215.7	217.3	221.8	230.1
127.5°	304.3	278.6	268.4	258.1	242.2	233.9	228.6	226.3	228.6	233.9	242.2
130°	315.7	290.7	280.4	270.2	254.4	245.3	238.5	236.2	238.5	245.3	254.4
132.5°	325.5	301.3	291.5	281.6	265.7	254.4	246.8	243.8	246.8	254.4	265.7
135°	335.3	311.9	301.6	291.4	275.5	264.2	255.9	252.8	255.9	264.2	275.5
137.5°	342.2	319.5	310.0	300.5	284.6	272.5	264.2	261.2	264.2	272.5	284.6
140°	349.0	327.0	317.6	308.1	293.0	280.8	273.3	269.5	273.3	280.8	293.0
142.5°	354.3	333.1	324.4	315.7	300.5	289.9	281.6	278.6	281.6	289.9	300.5
145°	358.8	339.1	330.4	321.7	308.9	297.5	290.7	288.4	290.7	297.5	308.9
147.5°	362.6	344.4	336.8	329.3	316.4	306.6	299.8	298.3	299.8	306.6	316.4
150°	366.4	349.0	342.2	335.3	324.8	314.9	308.9	308.1	308.9	314.9	324.8
152.5°	368.7	354.3	347.8	341.4	332.3	324.0	317.9	317.9	317.9	324.0	332.3
155°	371.7	358.8	353.5	348.2	339.9	332.3	327.8	327.8	327.8	332.3	339.9
157.5°	373.2	362.6	358.5	354.3	346.7	339.9	336.1	335.3	336.1	339.9	346.7
160°	375.5	366.4	362.6	358.8	353.5	347.5	344.4	344.4	344.4	347.5	353.5
162.5°	376.2	368.7	365.6	362.6	358.1	353.5	351.2	351.2	351.2	353.5	358.1
165°	377.0	370.9	368.2	365.6	362.6	358.8	357.3	358.1	357.3	358.8	362.6
167.5°	377.0	372.4	370.5	368.7	366.4	363.4	362.6	363.4	362.6	363.4	366.4
170°	376.2	372.4	371.6	370.9	369.4	367.1	366.4	367.9	366.4	367.1	369.4
172.5°	376.2	373.2	372.8	372.4	371.7	370.2	370.2	370.9	370.2	370.2	371.7
175°	375.5	374.0	373.6	373.2	373.2	371.7	372.4	373.2	372.4	371.7	373.2
177.5°	374.7	374.0	374.0	374.0	374.0	373.2	374.0	374.7	374.0	373.2	374.0
180°	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	872.2	868.4	866.9	863.1	854.0	848.0	841.2	836.6	837.4	833.6	835.9
5°	844.9	844.2	838.9	831.3	818.5	811.7	799.6	793.5	790.5	791.2	786.7
7.5°	822.2	815.4	811.7	799.6	787.4	773.1	763.2	757.9	753.4	748.9	745.8
10°	796.5	790.5	784.4	771.6	754.9	741.3	727.7	722.4	715.6	712.6	710.3
12.5°	769.3	765.5	757.9	742.8	723.9	711.0	695.2	692.1	683.1	677.0	675.5
15°	744.3	742.1	728.4	711.0	692.1	679.3	665.7	656.6	641.5	644.5	639.2
17.5°	717.9	708.0	699.7	676.3	667.2	647.5	631.6	627.1	616.5	609.7	602.9
20°	688.4	682.3	671.7	656.6	634.6	612.0	599.9	592.3	586.2	575.6	572.6
22.5°	660.4	652.8	643.7	624.1	605.1	586.2	569.6	562.8	555.2	547.7	543.1
25°	638.4	627.1	617.2	593.0	574.1	558.2	547.7	536.3	525.7	521.2	519.7
27.5°	604.4	597.6	587.7	565.1	547.7	530.3	520.4	512.9	501.5	496.2	491.7
30°	582.5	568.8	557.5	539.3	521.9	503.0	494.0	484.9	478.1	471.3	466.0
32.5°	553.0	542.4	533.3	515.1	497.7	480.3	470.5	456.9	453.1	447.8	441.8
35°	524.2	517.4	507.6	487.9	469.0	456.9	446.3	433.4	428.9	425.1	419.8
37.5°	497.0	487.1	480.3	461.4	444.8	430.4	422.1	411.5	408.5	403.9	400.2
40°	473.5	463.7	456.9	438.0	420.6	405.4	400.2	389.6	385.0	379.7	377.5
42.5°	447.1	438.7	429.7	416.0	397.9	382.8	372.2	366.1	360.1	357.8	353.3
45°	419.1	411.5	404.7	389.6	370.7	360.1	351.0	342.7	338.1	334.3	331.3
47.5°	394.9	388.1	379.0	362.3	347.2	337.4	328.3	320.0	315.4	310.9	307.1
50°	366.9	363.1	353.3	337.4	323.0	311.7	303.3	295.8	292.7	287.4	281.4
52.5°	341.9	335.1	326.8	313.9	301.1	287.4	276.1	271.6	266.3	263.2	257.9
55°	312.4	307.9	298.8	287.4	273.8	262.5	254.2	248.1	241.3	238.3	231.5
57.5°	287.4	279.1	274.6	260.2	247.4	236.0	230.0	223.9	216.3	211.8	208.8
60°	260.2	252.6	245.8	233.7	224.7	212.6	203.5	198.2	192.9	186.8	183.8
62.5°	233.7	227.7	219.4	209.5	198.2	188.4	181.5	174.0	171.0	164.9	162.6
65°	205.0	200.5	193.6	182.3	173.2	164.9	158.1	152.0	149.0	146.7	145.2
67.5°	179.3	173.2	168.7	158.9	149.0	142.2	138.4	134.6	130.9	128.6	126.3
70°	152.8	148.3	143.7	134.6	127.8	121.8	118.8	115.7	113.5	111.2	108.9
72.5°	125.6	123.3	118.8	112.7	107.4	102.9	100.6	96.8	94.6	90.8	89.3
75°	103.6	99.8	97.6	92.3	87.7	84.0	80.9	76.4	73.4	71.9	71.1
77.5°	81.7	80.2	77.2	72.6	70.3	66.6	62.0	60.5	59.0	59.0	58.2
80°	61.3	59.0	56.7	53.0	50.7	47.7	47.7	47.7	46.9	47.7	46.9
82.5°	41.6	40.1	38.6	36.3	35.6	35.6	36.3	36.3	36.3	36.3	36.3
85°	24.2	24.2	24.2	25.0	24.2	24.2	25.0	25.7	25.0	25.0	24.2
87.5°	11.3	11.3	12.1	12.1	12.9	12.9	12.9	12.9	12.9	12.9	13.6
90°	8.3	9.0	9.8	12.1	14.4	16.7	18.9	18.2	18.9	19.7	20.4
92.5°	38.6	45.4	52.2	76.5	116.6	155.9	140.8	105.2	74.9	58.3	50.7
95°	68.9	83.6	98.4	162.8	275.5	399.7	448.9	364.1	272.5	184.7	144.6
97.5°	79.5	95.8	112.0	175.6	306.6	515.5	690.4	713.8	626.0	472.4	372.4
100°	90.8	105.6	120.4	173.4	285.4	484.5	716.9	866.0	892.5	831.2	742.6
102.5°	103.7	117.0	130.2	176.4	267.2	439.1	667.7	873.6	981.1	993.9	951.5
105°	118.1	129.8	141.6	182.4	260.4	403.5	608.6	825.9	984.1	1059.8	1074.2
107.5°	134.0	145.0	155.9	192.3	258.9	377.7	556.4	757.8	938.7	1057.5	1116.6
110°	149.9	160.5	171.1	205.1	262.7	364.1	513.2	694.2	867.5	1006.8	1102.2

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	166.5	176.8	187.0	218.0	270.2	356.5	484.5	638.9	797.1	940.2	1050.0
115°	183.2	193.4	203.6	232.4	278.6	355.8	465.6	596.5	736.6	868.3	979.6
117.5°	199.8	209.3	218.8	247.5	289.2	356.5	452.7	568.5	689.6	806.2	908.4
120°	215.7	225.2	234.7	261.9	301.3	359.6	444.4	547.3	654.0	756.2	847.1
122.5°	230.1	240.4	250.6	277.1	312.6	364.9	439.1	529.9	626.0	716.1	798.6
125°	244.5	254.7	264.9	291.4	324.8	370.2	434.5	515.5	601.8	684.3	757.0
127.5°	258.1	268.4	278.6	304.3	334.6	376.2	432.2	501.9	579.9	654.8	721.4
130°	270.2	280.4	290.7	315.7	344.4	382.3	430.0	491.3	559.4	627.5	688.9
132.5°	281.6	291.5	301.3	325.5	353.5	386.8	429.2	481.4	540.5	601.8	657.8
135°	291.4	301.6	311.9	335.3	361.1	391.4	428.5	473.1	523.8	577.6	626.8
137.5°	300.5	310.0	319.5	342.2	367.1	394.4	426.9	465.6	507.9	553.4	597.3
140°	308.1	317.6	327.0	349.0	371.7	397.4	426.2	458.7	494.3	532.9	569.3
142.5°	315.7	324.4	333.1	354.3	376.2	399.7	424.7	452.7	481.4	513.2	543.5
145°	321.7	330.4	339.1	358.8	379.3	400.5	423.2	447.4	471.6	496.6	520.8
147.5°	329.3	336.8	344.4	362.6	381.5	400.5	420.9	442.1	463.3	483.7	504.2
150°	335.3	342.2	349.0	366.4	382.3	400.5	417.9	436.8	454.2	471.6	487.5
152.5°	341.4	347.8	354.3	368.7	383.8	398.2	414.1	430.7	445.9	460.3	473.9
155°	348.2	353.5	358.8	371.7	383.8	396.7	409.5	424.7	437.5	449.7	461.0
157.5°	354.3	358.5	362.6	373.2	384.6	394.4	405.7	417.9	428.5	439.1	448.1
160°	358.8	362.6	366.4	375.5	384.6	392.9	401.2	411.0	420.9	429.2	436.8
162.5°	362.6	365.6	368.7	376.2	383.8	389.9	396.7	404.2	411.8	418.6	425.4
165°	365.6	368.2	370.9	377.0	382.3	386.8	392.1	398.2	404.2	408.8	414.1
167.5°	368.7	370.5	372.4	377.0	381.5	383.8	387.6	392.1	397.4	401.2	404.2
170°	370.9	371.6	372.4	376.2	379.3	380.8	383.0	386.8	390.6	392.9	395.9
172.5°	372.4	372.8	373.2	376.2	378.5	378.5	379.3	381.5	384.6	386.1	388.3
175°	373.2	373.6	374.0	375.5	377.0	376.2	376.2	377.7	379.3	380.0	381.5
177.5°	374.0	374.0	374.0	374.7	376.2	374.7	374.0	374.7	375.5	376.2	377.0
180°	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.1	835.9	833.6	829.1	828.3	829.8	834.3	832.8	829.1	835.9	829.8
5°	789.0	785.2	783.7	785.2	780.6	778.4	782.9	780.6	782.9	783.7	785.9
7.5°	744.3	745.1	740.5	741.3	735.3	736.8	736.8	736.8	739.0	740.5	743.6
10°	705.8	707.3	702.0	702.7	698.2	695.2	697.4	702.0	702.0	702.0	703.5
12.5°	674.7	667.9	664.1	663.4	658.1	656.6	661.1	662.6	666.4	666.4	668.7
15°	636.2	634.6	631.6	631.6	618.8	621.8	623.3	628.6	636.2	630.1	631.6
17.5°	601.4	597.6	593.8	592.3	590.8	586.2	592.3	591.5	596.1	596.8	599.1
20°	570.4	567.3	559.8	560.5	562.0	555.2	559.0	559.0	563.5	568.1	573.4
22.5°	540.1	537.1	533.3	534.8	530.3	528.7	528.7	532.5	537.8	541.6	540.9
25°	516.6	511.3	509.1	506.8	504.5	506.1	503.8	507.6	511.3	513.6	511.3
27.5°	490.2	487.9	483.4	481.1	477.3	478.8	480.3	483.4	485.6	485.6	487.9
30°	464.5	461.4	459.9	457.6	457.6	454.6	455.4	458.4	460.7	462.9	466.0
32.5°	439.5	437.2	434.9	434.9	433.4	432.7	431.9	436.5	436.5	441.0	441.0
35°	419.1	415.3	415.3	411.5	413.0	412.3	410.7	413.8	414.5	417.6	416.8
37.5°	396.4	396.4	394.9	391.1	388.1	388.8	392.6	392.6	394.9	394.1	396.4
40°	373.7	372.2	372.2	369.9	369.1	368.4	369.1	369.9	373.7	372.9	373.7
42.5°	351.0	351.7	348.0	348.0	348.0	345.7	346.4	347.2	348.7	350.2	352.5
45°	329.0	327.5	326.8	325.3	323.8	324.5	323.8	326.8	326.0	327.5	329.8
47.5°	305.6	303.3	302.6	299.5	299.5	301.1	300.3	302.6	303.3	305.6	304.1
50°	282.9	279.9	277.6	278.4	273.8	275.3	275.3	277.6	279.9	280.6	282.1
52.5°	256.4	255.7	254.9	251.1	250.4	249.6	250.4	251.1	254.2	256.4	257.2
55°	230.7	230.0	225.4	223.9	221.6	221.6	223.1	223.9	229.2	230.0	233.0
57.5°	207.3	205.0	199.7	198.9	198.9	198.9	196.7	199.7	201.2	205.0	205.0
60°	181.5	181.5	177.0	177.0	177.8	177.0	177.0	177.8	177.8	180.8	182.3
62.5°	161.1	160.4	160.4	158.9	158.1	158.9	158.1	158.1	158.9	161.1	163.4
65°	143.0	142.2	141.5	140.7	139.2	139.2	139.9	141.5	141.5	143.0	143.7
67.5°	125.6	125.6	124.1	124.1	123.3	122.5	123.3	122.5	125.6	125.6	126.3
70°	108.2	107.4	105.1	104.4	102.1	102.9	102.9	105.1	105.9	107.4	108.9
72.5°	87.0	87.0	85.5	84.0	84.7	83.2	83.2	84.0	84.0	86.2	87.0
75°	71.9	70.3	69.6	70.3	69.6	71.1	69.6	69.6	71.1	71.1	71.1
77.5°	59.0	59.0	58.2	58.2	59.0	58.2	59.0	59.0	59.0	58.2	59.0
80°	48.4	47.7	47.7	47.7	46.9	46.9	46.9	46.9	46.9	46.9	46.9
82.5°	36.3	36.3	35.6	36.3	36.3	35.6	36.3	35.6	35.6	36.3	36.3
85°	24.2	25.7	24.2	24.2	25.0	25.0	25.7	25.0	25.7	24.2	25.0
87.5°	12.9	13.6	13.6	12.9	12.9	13.6	13.6	13.6	14.4	12.9	13.6
90°	21.2	22.0	21.2	22.0	22.7	22.0	22.7	22.0	21.2	22.0	21.2
92.5°	48.0	45.4	43.9	40.9	41.6	40.1	41.6	40.9	43.9	45.4	48.0
95°	131.0	117.3	103.0	96.1	90.8	87.8	90.8	96.1	103.0	117.3	131.0
97.5°	329.2	286.1	235.4	206.7	188.5	180.2	188.5	206.7	235.4	286.1	329.2
100°	688.8	635.1	558.7	503.4	473.9	474.6	473.9	503.4	558.7	635.1	688.8
102.5°	922.4	893.3	838.0	797.1	773.6	751.7	773.6	797.1	838.0	893.3	922.4
105°	1064.4	1054.5	1019.7	990.9	966.7	962.9	966.7	990.9	1019.7	1054.5	1064.4
107.5°	1126.8	1137.0	1132.5	1118.8	1109.0	1100.7	1109.0	1118.8	1132.5	1137.0	1126.8
110°	1128.7	1155.2	1176.4	1182.4	1180.9	1179.4	1180.9	1182.4	1176.4	1155.2	1128.7

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1086.0	1121.9	1165.0	1187.0	1194.5	1195.3	1194.5	1187.0	1165.0	1121.9	1086.0
115°	1020.8	1062.1	1118.8	1152.1	1167.3	1171.1	1167.3	1152.1	1118.8	1062.1	1020.8
117.5°	951.2	993.9	1053.0	1090.1	1112.8	1118.1	1112.8	1090.1	1053.0	993.9	951.2
120°	885.3	923.5	983.3	1025.7	1043.9	1048.4	1043.9	1025.7	983.3	923.5	885.3
122.5°	833.4	868.3	919.7	956.8	977.3	983.3	977.3	956.8	919.7	868.3	833.4
125°	787.3	817.6	866.0	899.3	918.2	923.5	918.2	899.3	866.0	817.6	787.3
127.5°	749.4	777.4	821.3	850.1	867.5	872.1	867.5	850.1	821.3	777.4	749.4
130°	714.6	740.3	780.5	807.7	823.6	829.7	823.6	807.7	780.5	740.3	714.6
132.5°	682.0	706.3	743.4	770.6	784.2	788.0	784.2	770.6	743.4	706.3	682.0
135°	648.3	669.9	707.0	729.7	743.4	748.7	743.4	729.7	707.0	669.9	648.3
137.5°	616.6	635.9	667.7	691.1	702.5	707.0	702.5	691.1	667.7	635.9	616.6
140°	585.6	601.8	630.6	651.8	663.9	663.1	663.9	651.8	630.6	601.8	585.6
142.5°	557.2	570.8	594.2	612.4	623.0	622.2	623.0	612.4	594.2	570.8	557.2
145°	531.8	542.8	561.7	577.6	583.6	585.2	583.6	577.6	561.7	542.8	531.8
147.5°	512.2	520.1	535.2	546.6	552.6	553.4	552.6	546.6	535.2	520.1	512.2
150°	494.7	501.9	513.2	521.6	526.1	526.1	526.1	521.6	513.2	501.9	494.7
152.5°	479.6	485.2	493.6	501.1	503.4	503.4	503.4	501.1	493.6	485.2	479.6
155°	465.6	470.1	476.9	483.0	484.5	485.2	484.5	483.0	476.9	470.1	465.6
157.5°	451.9	455.7	461.8	466.3	467.8	467.8	467.8	466.3	461.8	455.7	451.9
160°	439.4	442.1	447.4	451.9	451.9	451.2	451.9	451.9	447.4	442.1	439.4
162.5°	427.7	430.0	433.0	436.8	436.8	436.0	436.8	436.8	433.0	430.0	427.7
165°	416.0	417.9	420.9	423.9	423.2	423.2	423.2	423.9	420.9	417.9	416.0
167.5°	405.8	407.3	408.8	411.0	410.3	410.3	410.3	411.0	408.8	407.3	405.8
170°	396.6	397.4	398.2	399.7	398.9	398.9	398.9	399.7	398.2	397.4	396.6
172.5°	388.7	389.1	389.1	390.6	389.1	388.3	389.1	390.6	389.1	389.1	388.7
175°	381.5	381.5	381.5	382.3	381.5	380.8	381.5	382.3	381.5	381.5	381.5
177.5°	377.0	377.0	376.2	377.0	375.5	375.5	375.5	377.0	376.2	377.0	377.0
180°	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.9	838.9	835.9	829.8	835.9	839.6	843.4	849.5	852.5	852.5	857.0
5°	788.2	794.3	792.0	790.5	796.5	800.3	806.4	813.9	822.2	827.5	833.6
7.5°	745.8	749.6	753.4	753.4	759.5	767.8	776.9	785.9	796.5	804.1	808.6
10°	708.8	711.8	714.1	717.1	726.2	735.3	747.4	758.7	767.8	776.1	783.7
12.5°	673.2	677.8	683.1	685.3	692.1	703.5	714.8	728.4	742.8	751.1	758.7
15°	639.2	641.5	647.5	654.3	660.4	672.5	686.8	701.2	713.3	726.2	733.0
17.5°	604.4	605.1	621.0	617.2	636.9	648.3	655.8	669.4	689.1	699.7	710.3
20°	570.4	577.9	584.7	588.5	599.1	612.0	633.9	644.5	660.4	670.2	679.3
22.5°	543.9	555.2	555.2	564.3	569.6	581.7	597.6	618.0	635.4	642.2	655.1
25°	520.4	525.7	534.8	537.8	547.7	558.2	568.8	590.8	609.7	618.8	627.8
27.5°	490.2	497.0	509.1	509.1	521.9	533.3	546.1	560.5	579.4	592.3	602.1
30°	466.7	473.5	478.8	487.1	492.4	503.0	525.7	536.3	553.0	564.3	576.4
32.5°	444.8	450.1	454.6	463.7	469.7	481.8	494.0	512.9	527.2	537.8	550.7
35°	420.6	425.9	431.9	438.7	447.8	459.2	470.5	486.4	500.8	510.6	521.2
37.5°	397.9	401.7	410.7	415.3	422.8	433.4	447.8	464.5	477.3	484.9	495.5
40°	375.9	379.0	385.8	394.1	399.4	407.7	422.8	437.2	453.1	462.2	470.5
42.5°	352.5	356.3	362.3	370.7	379.0	388.1	396.4	413.0	427.4	434.9	444.0
45°	332.1	334.3	338.9	347.2	355.5	362.3	375.2	390.3	403.9	410.0	419.8
47.5°	307.9	310.1	316.9	320.7	329.8	338.9	351.7	366.9	379.0	385.0	394.1
50°	282.9	285.2	289.7	298.0	304.1	313.9	325.3	338.1	353.3	361.6	366.9
52.5°	258.7	263.2	267.0	273.8	281.4	291.2	301.8	313.9	326.8	335.1	341.2
55°	234.5	238.3	242.8	246.6	255.7	264.8	276.9	288.2	299.5	307.1	313.9
57.5°	207.3	212.6	217.1	224.7	231.5	239.0	252.6	261.7	275.3	280.6	286.7
60°	183.8	189.1	192.9	198.9	205.0	214.8	223.9	235.3	246.6	253.4	261.0
62.5°	164.1	166.4	168.7	174.7	180.8	189.9	198.9	210.3	222.4	226.2	232.2
65°	144.5	146.7	150.5	155.8	160.4	165.7	175.5	184.6	195.9	202.0	204.2
67.5°	127.8	130.1	130.9	134.6	138.4	144.5	149.8	158.9	169.4	173.2	177.8
70°	108.9	112.7	113.5	116.5	118.0	121.8	127.8	134.6	143.0	149.8	153.6
72.5°	87.0	92.3	93.8	98.3	100.6	104.4	108.9	114.2	119.5	122.5	125.6
75°	71.1	72.6	73.4	77.2	80.9	86.2	88.5	91.5	96.1	99.8	102.9
77.5°	59.0	59.8	60.5	60.5	61.3	64.3	68.8	72.6	75.6	77.2	79.4
80°	47.7	46.9	46.9	47.7	47.7	47.7	49.2	54.5	56.0	59.8	59.0
82.5°	37.1	35.6	36.3	35.6	35.6	35.6	35.6	36.3	36.3	38.6	40.1
85°	24.2	25.0	24.2	24.2	23.4	24.2	23.4	23.4	22.7	22.7	21.9
87.5°	12.9	13.6	12.9	12.9	12.1	12.9	12.1	12.1	11.3	11.3	9.8
90°	20.4	19.7	18.9	18.2	18.9	16.7	14.4	12.1	9.8	9.0	8.3
92.5°	50.7	58.3	74.9	105.2	140.8	155.9	116.6	76.5	52.2	45.4	38.6
95°	144.6	184.7	272.5	364.1	448.9	399.7	275.5	162.8	98.4	83.6	68.9
97.5°	372.4	472.4	626.0	713.8	690.4	515.5	306.6	175.6	112.0	95.8	79.5
100°	742.6	831.2	892.5	866.0	716.9	484.5	285.4	173.4	120.4	105.6	90.8
102.5°	951.5	993.9	981.1	873.6	667.7	439.1	267.2	176.4	130.2	117.0	103.7
105°	1074.2	1059.8	984.1	825.9	608.6	403.5	260.4	182.4	141.6	129.8	118.1
107.5°	1116.6	1057.5	938.7	757.8	556.4	377.7	258.9	192.3	155.9	145.0	134.0
110°	1102.2	1006.8	867.5	694.2	513.2	364.1	262.7	205.1	171.1	160.5	149.9

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1050.0	940.2	797.1	638.9	484.5	356.5	270.2	218.0	187.0	176.8	166.5
115°	979.6	868.3	736.6	596.5	465.6	355.8	278.6	232.4	203.6	193.4	183.2
117.5°	908.4	806.2	689.6	568.5	452.7	356.5	289.2	247.5	218.8	209.3	199.8
120°	847.1	756.2	654.0	547.3	444.4	359.6	301.3	261.9	234.7	225.2	215.7
122.5°	798.6	716.1	626.0	529.9	439.1	364.9	312.6	277.1	250.6	240.4	230.1
125°	757.0	684.3	601.8	515.5	434.5	370.2	324.8	291.4	264.9	254.7	244.5
127.5°	721.4	654.8	579.9	501.9	432.2	376.2	334.6	304.3	278.6	268.4	258.1
130°	688.9	627.5	559.4	491.3	430.0	382.3	344.4	315.7	290.7	280.4	270.2
132.5°	657.8	601.8	540.5	481.4	429.2	386.8	353.5	325.5	301.3	291.5	281.6
135°	626.8	577.6	523.8	473.1	428.5	391.4	361.1	335.3	311.9	301.6	291.4
137.5°	597.3	553.4	507.9	465.6	426.9	394.4	367.1	342.2	319.5	310.0	300.5
140°	569.3	532.9	494.3	458.7	426.2	397.4	371.7	349.0	327.0	317.6	308.1
142.5°	543.5	513.2	481.4	452.7	424.7	399.7	376.2	354.3	333.1	324.4	315.7
145°	520.8	496.6	471.6	447.4	423.2	400.5	379.3	358.8	339.1	330.4	321.7
147.5°	504.2	483.7	463.3	442.1	420.9	400.5	381.5	362.6	344.4	336.8	329.3
150°	487.5	471.6	454.2	436.8	417.9	400.5	382.3	366.4	349.0	342.2	335.3
152.5°	473.9	460.3	445.9	430.7	414.1	398.2	383.8	368.7	354.3	347.8	341.4
155°	461.0	449.7	437.5	424.7	409.5	396.7	383.8	371.7	358.8	353.5	348.2
157.5°	448.1	439.1	428.5	417.9	405.7	394.4	384.6	373.2	362.6	358.5	354.3
160°	436.8	429.2	420.9	411.0	401.2	392.9	384.6	375.5	366.4	362.6	358.8
162.5°	425.4	418.6	411.8	404.2	396.7	389.9	383.8	376.2	368.7	365.6	362.6
165°	414.1	408.8	404.2	398.2	392.1	386.8	382.3	377.0	370.9	368.2	365.6
167.5°	404.2	401.2	397.4	392.1	387.6	383.8	381.5	377.0	372.4	370.5	368.7
170°	395.9	392.9	390.6	386.8	383.0	380.8	379.3	376.2	372.4	371.6	370.9
172.5°	388.3	386.1	384.6	381.5	379.3	378.5	378.5	376.2	373.2	372.8	372.4
175°	381.5	380.0	379.3	377.7	376.2	376.2	377.0	375.5	374.0	373.6	373.2
177.5°	377.0	376.2	375.5	374.7	374.0	374.7	376.2	374.7	374.0	374.0	374.0
180°	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0	374.0

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	883.5	883.5	883.5	883.5
2.5°	860.8	866.1	876.7	885.8
5°	842.7	851.0	866.9	882.8
7.5°	820.7	833.6	854.0	876.0
10°	799.6	816.2	841.2	866.9
12.5°	778.4	795.8	822.2	855.5
15°	753.4	771.6	803.3	843.4
17.5°	731.5	755.7	784.4	824.5
20°	708.0	726.2	763.2	805.6
22.5°	678.5	708.8	743.6	788.2
25°	655.1	681.5	716.3	767.0
27.5°	626.3	657.3	699.7	744.3
30°	602.9	628.6	667.9	721.6
32.5°	575.6	605.9	646.8	699.7
35°	551.4	577.2	615.7	669.4
37.5°	522.7	550.7	593.8	641.5
40°	497.7	525.0	565.8	610.4
42.5°	467.5	496.2	537.1	574.9
45°	443.3	469.7	502.3	537.1
47.5°	413.8	441.8	473.5	497.7
50°	387.3	413.0	438.0	458.4
52.5°	358.5	382.0	404.7	419.8
55°	332.1	350.2	368.4	379.0
57.5°	301.1	318.5	333.6	339.6
60°	273.8	288.2	298.0	304.8
62.5°	245.1	255.7	263.2	267.0
65°	217.1	224.7	228.4	232.2
67.5°	188.4	195.2	197.4	202.0
70°	158.1	165.7	167.2	169.4
72.5°	135.4	135.4	138.4	141.5
75°	108.2	109.7	111.2	111.2
77.5°	84.7	84.7	86.2	87.0
80°	62.0	62.8	62.8	62.0
82.5°	42.4	43.9	42.4	41.6
85°	23.4	26.5	25.0	25.0
87.5°	9.8	9.8	11.3	9.8
90°	6.8	4.5	3.0	1.5
92.5°	31.0	24.2	16.7	11.4
95°	49.2	36.3	28.0	25.7
97.5°	59.8	48.4	41.6	40.9
100°	72.7	62.1	56.8	56.0
102.5°	87.8	78.0	73.4	71.9
105°	103.7	94.6	90.1	87.8
107.5°	120.4	111.3	106.7	104.5
110°	137.0	128.7	124.9	122.6

TEST NUMBER: P1012672

CATALOG NUMBER: S123RDIP-B560D805UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	153.7	145.3	141.6	139.3
115°	170.3	162.8	158.2	155.2
117.5°	185.5	178.7	174.9	171.1
120°	201.4	193.8	190.0	187.7
122.5°	216.5	208.2	204.4	202.1
125°	230.1	221.8	217.3	215.7
127.5°	242.2	233.9	228.6	226.3
130°	254.4	245.3	238.5	236.2
132.5°	265.7	254.4	246.8	243.8
135°	275.5	264.2	255.9	252.8
137.5°	284.6	272.5	264.2	261.2
140°	293.0	280.8	273.3	269.5
142.5°	300.5	289.9	281.6	278.6
145°	308.9	297.5	290.7	288.4
147.5°	316.4	306.6	299.8	298.3
150°	324.8	314.9	308.9	308.1
152.5°	332.3	324.0	317.9	317.9
155°	339.9	332.3	327.8	327.8
157.5°	346.7	339.9	336.1	335.3
160°	353.5	347.5	344.4	344.4
162.5°	358.1	353.5	351.2	351.2
165°	362.6	358.8	357.3	358.1
167.5°	366.4	363.4	362.6	363.4
170°	369.4	367.1	366.4	367.9
172.5°	371.7	370.2	370.2	370.9
175°	373.2	371.7	372.4	373.2
177.5°	374.0	373.2	374.0	374.7
180°	374.0	374.0	374.0	374.0

(END OF REPORT)