

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012687

Luminaire Tested: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012687
REPORT IS A COMBINATION OF REPORTS P993508 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D805UB40-4F0-XX-W2A-A1
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4886.0 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45	45	45
1	97	93	89	86	89	86	82	80	71	69	67	58	57	56	47	46	45	39	39	39
2	89	82	76	71	81	75	70	66	63	60	57	52	49	47	42	40	38	34	34	34
3	81	72	66	60	75	67	61	56	56	52	48	46	43	41	37	35	33	29	29	29
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29	25	25	25
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	22	22	22
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20	20	20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	20	18	18	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18	16	16	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15	15	15
10	48	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9536	9536	9536	9536
5°	9544	10983	9567	8148
10°	9459	13257	9500	7117
15°	9361	15047	9361	6275
20°	9170	16230	9221	5566
25°	9029	15420	9011	5079
30°	8866	10684	8847	4603
35°	8669	6859	8629	4244
40°	8424	4844	8383	3886
45°	7997	3876	7987	3538
50°	7474	3243	7449	3131
55°	6885	2673	6831	2654
60°	6308	2209	6244	2257
65°	5630	1767	5666	1914
70°	5003	1228	5139	1547
75°	4241	911	4413	1190
80°	3377	605	3665	891
85°	2401	286	2622	554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 12731 cd/sqm

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.8
10°-20°	272.3	5.6
20°-30°	428.9	8.8
30°-40°	446.0	9.1
40°-50°	381.6	7.8
50°-60°	290.9	6.0
60°-70°	186.4	3.8
70°-80°	89.3	1.8
80°-90°	25.5	0.5
90°-100°	62.2	1.3
100°-110°	188.3	3.9
110°-120°	320.6	6.6
120°-130°	421.7	8.6
130°-140°	474.0	9.7
140°-150°	466.0	9.5
150°-160°	392.4	8.0
160°-170°	261.2	5.3
170°-180°	91.5	1.9
0°-30°	788.3	16.1
0°-40°	1234.3	25.3
0°-60°	1906.8	39.0
0°-90°	2208.0	45.2
90°-120°	571.1	11.7
90°-150°	1932.9	39.6
90°-180°	2678.0	54.8
0°-180°	4886.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	886	886	886	886	886	
5°	885	1052	887	780	885	84
15°	846	1495	846	624	846	238
25°	769	1540	768	507	769	354
35°	671	668	668	413	671	420
45°	538	356	538	325	538	415
55°	380	224	377	222	380	341
65°	233	129	234	140	233	233
75°	112	55	116	71	112	120
85°	25	13	27	25	25	28
90°	1	23	1	23	1	5
95°	45	59	45	59	45	49
105°	171	181	171	181	171	183
115°	323	323	323	323	323	319
125°	472	467	472	467	472	421
135°	613	612	613	612	613	472
145°	743	743	743	743	743	464
155°	851	850	851	850	851	392
165°	927	924	927	924	927	261
175°	964	960	964	960	964	92
180°	966	966	966	966	966	

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9
2.5°	888.2	894.3	898.8	901.9	909.4	914.0	917.8	924.6	924.6	926.1	929.2
5°	885.2	898.1	907.2	919.3	935.2	942.8	953.4	962.5	975.4	982.3	989.1
7.5°	878.3	896.5	915.5	933.7	957.2	972.4	983.0	1006.5	1023.2	1043.7	1059.6
10°	869.2	894.3	918.5	946.6	978.5	1001.2	1017.1	1048.2	1080.1	1108.9	1133.2
12.5°	857.9	888.2	923.1	957.2	1002.0	1024.7	1050.5	1089.2	1134.7	1171.1	1203.7
15°	845.7	880.6	920.1	961.8	1017.9	1049.8	1086.9	1134.0	1184.8	1237.1	1281.9
17.5°	826.8	870.8	914.7	975.4	1041.4	1060.4	1092.2	1156.7	1219.7	1266.7	1321.3
20°	807.8	857.1	912.5	967.1	1038.4	1082.4	1112.0	1180.2	1247.7	1304.6	1357.0
22.5°	790.4	841.9	899.6	968.6	1035.3	1079.3	1116.5	1187.8	1265.9	1329.6	1394.1
25°	769.1	825.2	889.0	954.2	1035.3	1068.7	1109.7	1192.4	1275.0	1348.6	1428.2
27.5°	746.4	803.2	866.2	933.0	1007.3	1056.6	1096.8	1185.5	1286.4	1365.3	1447.2
30°	723.6	782.0	842.7	902.6	986.0	1033.1	1079.3	1177.2	1292.5	1382.7	1445.7
32.5°	701.6	750.9	810.8	869.2	951.9	1003.5	1055.8	1168.8	1294.8	1370.6	1400.9
35°	671.3	722.8	771.4	833.6	917.0	967.8	1029.3	1168.1	1284.9	1331.9	1316.8
37.5°	643.2	686.4	732.7	788.1	873.8	939.8	1003.5	1148.4	1252.3	1255.3	1169.6
40°	612.1	647.8	686.4	744.8	837.4	902.6	971.6	1118.0	1193.1	1148.4	997.4
42.5°	576.5	608.3	638.7	695.5	796.4	869.2	943.6	1080.1	1107.4	1004.2	847.2
45°	538.5	564.3	592.4	652.3	753.2	825.2	899.6	1021.7	993.6	848.0	698.6
47.5°	499.1	521.1	548.4	603.0	706.9	780.5	851.0	938.3	867.0	710.7	585.6
50°	459.6	477.1	503.6	559.8	659.9	726.6	791.9	848.8	748.6	609.8	483.9
52.5°	421.0	434.6	461.9	509.7	606.8	670.5	717.5	739.5	637.9	503.6	420.2
55°	380.0	395.2	413.4	461.9	558.3	605.3	636.4	635.6	530.9	427.0	347.4
57.5°	340.6	354.2	370.1	418.7	496.8	528.7	555.2	542.3	443.0	349.7	298.1
60°	305.7	313.3	330.7	371.7	430.8	458.1	473.3	451.3	361.8	295.1	246.5
62.5°	267.7	275.3	289.7	328.4	364.8	379.2	392.1	364.1	298.8	240.4	210.9
65°	232.9	242.7	251.8	282.9	302.6	320.1	318.6	295.1	233.6	195.7	171.4
67.5°	202.5	206.3	213.9	232.9	242.0	254.9	255.6	229.1	188.1	159.3	144.9
70°	169.9	173.7	179.0	188.1	194.2	197.2	195.7	172.2	141.8	124.4	111.5
72.5°	141.8	141.1	144.9	144.9	150.9	150.2	145.6	127.4	107.7	93.3	85.7
75°	111.5	112.3	113.0	111.5	109.2	106.2	102.4	88.7	75.8	69.0	62.2
77.5°	87.2	85.7	86.5	81.2	78.1	75.1	69.8	63.0	52.3	50.8	47.8
80°	62.2	61.4	60.7	58.4	51.6	48.5	44.8	41.0	38.7	37.2	36.4
82.5°	41.7	41.7	40.2	35.6	31.9	29.6	28.8	27.3	25.0	25.0	24.3
85°	25.0	24.3	22.8	18.2	15.9	15.9	15.9	15.9	14.4	14.4	13.7
87.5°	9.9	9.1	6.8	6.8	6.1	6.1	6.1	5.3	5.3	4.6	4.6
90°	0.8	2.5	4.2	5.9	7.6	8.4	9.5	11.7	13.8	16.0	18.2
92.5°	22.8	23.8	24.8	25.8	26.8	27.3	27.8	28.8	29.9	30.9	31.9
95°	44.8	46.0	47.2	48.3	49.5	50.1	50.8	52.1	53.5	54.8	56.2
97.5°	73.6	74.4	75.3	76.1	77.0	77.4	77.9	78.9	80.0	81.0	82.0
100°	103.3	104.3	105.3	106.3	107.3	107.8	108.2	109.1	109.9	110.8	111.6
102.5°	137.4	137.9	138.4	138.9	139.4	139.7	140.3	141.5	142.6	143.8	145.0
105°	170.8	171.1	171.5	171.8	172.1	172.3	173.1	174.6	176.1	177.7	179.2
107.5°	210.3	210.5	210.7	210.8	211.0	211.1	211.4	212.1	212.8	213.4	214.1
110°	246.7	247.1	247.4	247.8	248.1	248.3	248.5	248.8	249.1	249.5	249.8

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	284.7	284.9	285.1	285.2	285.4	285.5	285.5	285.5	285.5	285.5	285.5
115°	322.7	323.2	323.7	324.2	324.7	324.9	324.7	324.4	324.1	323.7	323.4
117.5°	361.4	361.6	361.7	361.9	362.0	362.1	361.9	361.6	361.3	360.9	360.6
120°	397.1	398.1	399.1	400.1	401.1	401.6	401.2	400.3	399.5	398.6	397.8
122.5°	434.3	435.0	435.6	436.3	437.0	437.3	437.1	436.8	436.5	436.1	435.8
125°	472.2	472.7	473.2	473.7	474.2	474.5	474.3	474.0	473.7	473.3	473.0
127.5°	507.2	508.2	509.2	510.2	511.2	511.7	511.5	511.2	510.9	510.5	510.2
130°	542.1	543.5	544.8	546.2	547.5	548.2	547.9	547.4	546.9	546.4	545.9
132.5°	577.0	578.4	579.7	581.1	582.4	583.1	582.9	582.6	582.3	581.9	581.6
135°	612.7	613.7	614.7	615.7	616.7	617.2	617.1	617.0	616.8	616.7	616.5
137.5°	645.3	646.1	647.0	647.8	648.7	649.1	649.4	649.9	650.4	650.9	651.4
140°	679.5	680.3	681.2	682.0	682.9	683.3	683.4	683.6	683.7	683.9	684.1
142.5°	710.6	711.4	712.3	713.1	714.0	714.4	714.6	714.9	715.2	715.6	715.9
145°	743.3	743.6	744.0	744.3	744.6	744.8	745.1	745.6	746.1	746.6	747.1
147.5°	771.4	772.1	772.7	773.4	774.1	774.4	774.7	775.2	775.7	776.2	776.7
150°	801.0	801.3	801.7	802.0	802.3	802.5	802.7	803.0	803.3	803.7	804.0
152.5°	825.3	825.8	826.3	826.8	827.3	827.5	827.6	827.8	827.9	828.1	828.3
155°	851.1	851.1	851.1	851.1	851.1	851.1	851.2	851.3	851.5	851.6	851.8
157.5°	873.1	872.9	872.7	872.6	872.4	872.3	872.4	872.6	872.7	872.9	873.1
160°	893.6	893.3	892.9	892.6	892.3	892.1	892.1	892.1	892.1	892.1	892.1
162.5°	911.8	911.3	910.8	910.3	909.8	909.5	909.6	909.8	909.9	910.1	910.3
165°	927.0	926.5	926.0	925.5	925.0	924.7	924.7	924.7	924.7	924.7	924.7
167.5°	939.9	939.2	938.6	937.9	937.2	936.9	937.0	937.1	937.3	937.4	937.6
170°	950.5	949.8	949.2	948.5	947.8	947.5	947.5	947.5	947.5	947.5	947.5
172.5°	958.9	958.2	957.6	956.9	956.2	955.9	955.9	955.9	955.9	955.9	955.9
175°	964.2	963.5	962.9	962.2	961.5	961.2	961.2	961.2	961.2	961.2	961.2
177.5°	967.2	966.5	965.9	965.2	964.5	964.2	964.2	964.2	964.2	964.2	964.2
180°	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9
2.5°	935.2	935.2	942.1	948.9	945.1	947.4	955.7	952.7	958.7	958.0	960.3
5°	1005.8	1014.1	1020.9	1035.3	1037.6	1035.3	1049.8	1053.6	1060.4	1052.0	1055.8
7.5°	1085.4	1102.9	1119.5	1140.8	1147.6	1149.1	1156.7	1167.3	1176.4	1159.7	1168.1
10°	1162.8	1189.3	1223.5	1242.4	1259.1	1265.2	1271.2	1278.1	1288.7	1298.5	1291.0
12.5°	1246.2	1284.9	1317.5	1351.6	1372.1	1369.8	1387.3	1391.8	1400.2	1402.5	1405.5
15°	1314.5	1369.1	1389.6	1440.4	1444.9	1460.1	1479.8	1497.3	1499.5	1495.0	1495.0
17.5°	1379.7	1426.7	1463.1	1504.1	1512.4	1525.3	1550.4	1558.7	1561.7	1561.0	1561.0
20°	1432.8	1463.9	1525.3	1559.5	1573.1	1589.8	1607.3	1617.9	1620.1	1623.2	1618.6
22.5°	1467.7	1514.7	1564.8	1592.8	1604.2	1610.3	1621.7	1624.7	1620.9	1621.7	1622.4
25°	1495.0	1541.3	1571.6	1579.2	1578.4	1570.8	1562.5	1548.1	1546.6	1540.5	1528.4
27.5°	1502.6	1520.0	1516.2	1485.1	1454.0	1451.0	1400.9	1373.6	1342.5	1347.1	1329.6
30°	1461.6	1438.9	1385.0	1306.1	1273.5	1220.4	1164.3	1105.9	1083.1	1058.1	1104.4
32.5°	1361.5	1280.3	1184.8	1082.4	1027.8	980.7	920.8	878.3	854.1	833.6	873.0
35°	1210.6	1083.9	957.2	860.1	815.4	772.9	716.8	695.5	665.2	668.2	672.0
37.5°	1016.4	876.8	781.3	685.7	656.1	638.7	597.7	565.1	554.5	551.4	551.4
40°	834.3	719.8	634.9	559.8	537.0	522.6	490.0	474.8	463.4	460.4	464.2
42.5°	690.2	592.4	526.4	476.3	460.4	442.2	428.6	409.6	407.3	402.0	408.8
45°	579.5	494.5	445.2	408.8	395.2	388.4	373.2	361.8	357.3	356.5	361.8
47.5°	491.5	425.5	382.3	359.5	348.9	342.1	329.2	324.6	320.1	321.6	319.3
50°	412.6	363.3	335.3	314.8	307.9	301.1	292.8	288.2	286.0	286.0	285.2
52.5°	354.2	313.3	295.1	276.1	273.1	269.3	260.2	257.1	253.3	252.6	255.6
55°	303.4	275.3	257.1	245.8	242.7	235.1	231.3	227.5	225.3	223.8	224.5
57.5°	259.4	238.2	226.0	216.2	210.9	207.8	201.0	200.2	198.7	198.7	198.0
60°	223.0	207.8	193.4	187.3	183.6	179.8	179.0	174.5	172.2	173.7	172.9
62.5°	188.9	176.7	168.4	161.6	159.3	156.3	154.0	152.5	150.2	150.9	150.9
65°	157.8	147.9	141.8	135.8	135.0	132.0	131.2	129.7	129.7	128.9	130.5
67.5°	129.7	122.9	117.6	113.8	111.5	112.3	109.2	106.9	106.9	106.2	108.5
70°	103.2	99.4	94.1	89.5	86.5	86.5	82.7	81.9	81.9	81.9	81.2
72.5°	79.6	72.8	70.5	69.0	69.0	69.0	67.5	67.5	66.7	67.5	66.7
75°	59.2	58.4	56.9	56.1	56.1	55.4	54.6	54.6	54.6	54.6	54.6
77.5°	46.3	46.3	44.8	44.0	44.0	44.0	43.2	43.2	42.5	42.5	42.5
80°	34.1	34.1	32.6	32.6	32.6	31.9	31.9	31.9	32.6	31.9	31.9
82.5°	23.5	23.5	22.8	23.5	22.8	22.0	22.0	22.0	21.2	22.0	22.0
85°	13.7	13.7	12.9	12.1	12.9	12.9	12.1	12.9	12.1	12.9	12.1
87.5°	5.3	4.6	4.6	4.6	3.8	4.6	3.8	3.8	4.6	3.8	4.6
90°	18.9	19.6	20.3	21.0	21.3	21.5	21.8	22.1	22.5	22.8	22.5
92.5°	32.4	32.9	33.4	33.9	34.2	34.0	33.7	33.3	33.0	32.6	33.0
95°	56.9	57.5	58.2	58.9	59.2	59.2	59.2	59.2	59.2	59.2	59.2
97.5°	82.8	83.7	84.5	85.4	85.8	85.7	85.5	85.4	85.2	85.0	85.2
100°	112.1	112.6	113.1	113.6	113.9	114.1	114.4	114.7	115.1	115.4	115.1
102.5°	145.5	146.0	146.5	147.0	147.3	147.2	147.0	146.9	146.7	146.5	146.7
105°	179.2	179.2	179.2	179.2	179.2	179.4	179.7	180.0	180.4	180.7	180.4
107.5°	214.6	215.1	215.6	216.1	216.4	216.3	216.1	216.0	215.8	215.6	215.8
110°	250.5	251.1	251.8	252.5	252.8	252.6	252.3	252.0	251.6	251.3	251.6

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	286.3	287.2	288.0	288.9	289.3	289.3	289.3	289.3	289.3	289.3	289.3
115°	323.6	323.8	323.9	324.1	324.2	324.1	323.9	323.8	323.6	323.4	323.6
117.5°	360.6	360.6	360.6	360.6	360.6	360.4	359.9	359.4	358.9	358.4	358.9
120°	397.6	397.5	397.3	397.2	397.1	396.9	396.6	396.3	395.9	395.6	395.9
122.5°	435.3	434.8	434.3	433.8	433.5	433.2	432.7	432.2	431.7	431.2	431.7
125°	472.3	471.7	471.0	470.3	470.0	469.7	469.0	468.3	467.6	466.9	467.6
127.5°	509.2	508.2	507.1	506.1	505.6	505.3	504.6	503.9	503.3	502.6	503.3
130°	545.2	544.5	543.8	543.1	542.8	542.2	541.0	539.9	538.7	537.5	538.7
132.5°	580.8	579.9	579.1	578.2	577.8	577.4	576.5	575.7	574.8	574.0	574.8
135°	615.8	615.1	614.4	613.7	613.4	613.2	612.9	612.6	612.2	611.9	612.2
137.5°	650.6	649.7	648.9	648.0	647.6	647.3	646.8	646.3	645.8	645.3	645.8
140°	683.9	683.7	683.6	683.4	683.3	682.7	681.5	680.4	679.2	678.0	679.2
142.5°	715.7	715.6	715.4	715.3	715.2	714.8	713.9	713.1	712.2	711.4	712.2
145°	746.9	746.7	746.6	746.4	746.3	746.0	745.3	744.6	744.0	743.3	744.0
147.5°	776.7	776.7	776.7	776.7	776.7	776.2	775.2	774.1	773.1	772.1	773.1
150°	804.0	804.0	804.0	804.0	804.0	803.5	802.5	801.5	800.5	799.5	800.5
152.5°	828.6	829.0	829.3	829.6	829.8	829.4	828.5	827.7	826.8	826.0	826.8
155°	852.5	853.2	853.9	854.6	854.9	854.3	853.1	852.0	850.8	849.6	850.8
157.5°	873.8	874.4	875.1	875.8	876.1	875.6	874.6	873.6	872.6	871.6	872.6
160°	892.9	893.8	894.6	895.5	895.9	895.6	894.9	894.2	893.5	892.8	893.5
162.5°	911.1	912.0	912.8	913.7	914.1	913.5	912.3	911.2	910.0	908.8	910.0
165°	925.7	926.7	927.8	928.8	929.3	928.7	927.5	926.4	925.2	924.0	925.2
167.5°	938.6	939.6	940.7	941.7	942.2	941.7	940.7	939.6	938.6	937.6	938.6
170°	948.7	949.9	951.0	952.2	952.8	952.2	951.0	949.9	948.7	947.5	948.7
172.5°	956.9	957.9	958.9	959.9	960.4	959.8	958.6	957.5	956.3	955.1	956.3
175°	962.2	963.2	964.2	965.2	965.7	965.1	963.9	962.8	961.6	960.4	961.6
177.5°	965.2	966.2	967.3	968.3	968.8	968.2	967.0	965.8	964.6	963.4	964.6
180°	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9
2.5°	956.5	951.9	948.9	946.6	944.3	951.2	942.1	932.2	925.4	920.8	919.3
5°	1056.6	1046.7	1038.4	1031.6	1033.1	1033.1	1017.1	999.7	984.5	976.2	967.1
7.5°	1172.6	1162.0	1145.3	1141.5	1138.5	1119.5	1103.6	1071.8	1052.8	1033.8	1017.1
10°	1287.9	1274.3	1258.3	1253.0	1245.5	1221.9	1197.7	1156.7	1133.2	1098.3	1076.3
12.5°	1395.6	1378.9	1363.0	1359.2	1347.8	1327.4	1285.7	1243.2	1203.0	1165.8	1127.1
15°	1485.9	1481.3	1457.1	1441.9	1416.9	1388.8	1379.7	1322.1	1271.2	1232.6	1162.8
17.5°	1561.7	1540.5	1517.8	1507.9	1498.0	1465.4	1432.8	1373.6	1319.0	1262.1	1217.4
20°	1622.4	1598.9	1583.0	1568.6	1564.0	1526.9	1475.3	1422.9	1363.0	1299.3	1240.9
22.5°	1625.5	1622.4	1611.8	1603.5	1594.4	1570.1	1529.1	1463.9	1400.2	1330.4	1253.8
25°	1562.5	1558.0	1588.3	1580.7	1586.8	1577.7	1555.7	1501.1	1426.7	1344.8	1267.4
27.5°	1372.9	1419.1	1466.9	1483.6	1495.0	1527.6	1538.2	1507.9	1448.0	1360.7	1274.3
30°	1115.0	1176.4	1253.8	1295.5	1327.4	1388.0	1466.9	1476.8	1448.7	1378.9	1272.8
32.5°	875.3	931.4	993.6	1042.9	1085.4	1209.8	1316.0	1392.6	1406.3	1369.8	1276.5
35°	705.4	729.7	788.8	835.9	893.5	999.7	1124.9	1248.5	1331.9	1336.5	1265.2
37.5°	581.8	594.7	646.2	672.8	706.9	800.2	917.0	1078.6	1208.3	1269.7	1233.3
40°	481.6	511.2	540.8	556.0	580.2	644.7	757.0	883.6	1044.4	1158.2	1184.0
42.5°	417.9	430.8	449.8	471.0	486.2	542.3	617.4	733.5	878.3	1036.9	1108.2
45°	368.6	373.2	392.9	406.6	422.5	461.9	515.0	612.1	739.5	895.8	1017.1
47.5°	327.7	336.8	347.4	355.7	366.4	396.7	442.2	512.7	625.0	764.6	895.0
50°	291.3	296.6	310.2	314.0	321.6	342.8	377.7	431.6	524.1	635.6	770.6
52.5°	257.1	267.0	272.3	277.6	284.4	301.9	324.6	368.6	438.4	543.1	657.6
55°	230.6	233.6	241.2	245.8	251.1	263.2	282.9	315.5	370.1	453.6	562.0
57.5°	204.8	204.8	212.4	216.2	221.5	230.6	248.0	273.1	312.5	374.7	474.1
60°	177.5	178.2	184.3	188.9	190.4	199.5	213.9	233.6	264.0	309.5	390.6
62.5°	153.2	157.0	160.0	161.6	166.9	172.2	184.3	198.0	219.2	259.4	317.1
65°	132.7	133.5	135.8	137.3	139.6	145.6	154.7	163.8	182.0	211.6	258.6
67.5°	109.2	112.3	115.3	115.3	117.6	120.6	129.7	137.3	150.9	168.4	200.2
70°	81.9	83.4	88.0	90.3	93.3	98.6	103.2	107.7	118.3	131.2	155.5
72.5°	68.3	68.3	69.8	70.5	70.5	74.3	81.2	85.7	91.0	100.1	116.8
75°	54.6	54.6	56.9	56.1	57.6	59.2	59.9	63.0	66.0	72.8	82.7
77.5°	43.2	44.0	44.0	44.8	44.8	45.5	46.3	47.8	49.3	53.1	57.6
80°	31.9	32.6	32.6	33.4	33.4	34.1	34.9	35.6	37.2	38.7	41.0
82.5°	22.0	22.8	22.8	23.5	22.8	23.5	24.3	24.3	25.0	26.5	27.3
85°	12.9	12.9	13.7	12.9	12.9	12.9	13.7	13.7	14.4	16.7	16.7
87.5°	3.8	4.6	3.8	4.6	4.6	4.6	4.6	5.3	5.3	6.1	6.8
90°	22.1	21.8	21.5	21.3	21.0	20.3	19.6	18.9	18.2	16.0	13.8
92.5°	33.3	33.7	34.0	34.2	33.9	33.4	32.9	32.4	31.9	30.9	29.9
95°	59.2	59.2	59.2	59.2	58.9	58.2	57.5	56.9	56.2	54.8	53.5
97.5°	85.4	85.5	85.7	85.8	85.4	84.5	83.7	82.8	82.0	81.0	80.0
100°	114.7	114.4	114.1	113.9	113.6	113.1	112.6	112.1	111.6	110.8	109.9
102.5°	146.9	147.0	147.2	147.3	147.0	146.5	146.0	145.5	145.0	143.8	142.6
105°	180.0	179.7	179.4	179.2	179.2	179.2	179.2	179.2	179.2	177.7	176.1
107.5°	216.0	216.1	216.3	216.4	216.1	215.6	215.1	214.6	214.1	213.4	212.8
110°	252.0	252.3	252.6	252.8	252.5	251.8	251.1	250.5	249.8	249.5	249.1

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	289.3	289.3	289.3	289.3	288.9	288.0	287.2	286.3	285.5	285.5	285.5
115°	323.8	323.9	324.1	324.2	324.1	323.9	323.8	323.6	323.4	323.7	324.1
117.5°	359.4	359.9	360.4	360.6	360.6	360.6	360.6	360.6	360.6	360.9	361.3
120°	396.3	396.6	396.9	397.1	397.2	397.3	397.5	397.6	397.8	398.6	399.5
122.5°	432.2	432.7	433.2	433.5	433.8	434.3	434.8	435.3	435.8	436.1	436.5
125°	468.3	469.0	469.7	470.0	470.3	471.0	471.7	472.3	473.0	473.3	473.7
127.5°	503.9	504.6	505.3	505.6	506.1	507.1	508.2	509.2	510.2	510.5	510.9
130°	539.9	541.0	542.2	542.8	543.1	543.8	544.5	545.2	545.9	546.4	546.9
132.5°	575.7	576.5	577.4	577.8	578.2	579.1	579.9	580.8	581.6	581.9	582.3
135°	612.6	612.9	613.2	613.4	613.7	614.4	615.1	615.8	616.5	616.7	616.8
137.5°	646.3	646.8	647.3	647.6	648.0	648.9	649.7	650.6	651.4	650.9	650.4
140°	680.4	681.5	682.7	683.3	683.4	683.6	683.7	683.9	684.1	683.9	683.7
142.5°	713.1	713.9	714.8	715.2	715.3	715.4	715.6	715.7	715.9	715.6	715.2
145°	744.6	745.3	746.0	746.3	746.4	746.6	746.7	746.9	747.1	746.6	746.1
147.5°	774.1	775.2	776.2	776.7	776.7	776.7	776.7	776.7	776.7	776.2	775.7
150°	801.5	802.5	803.5	804.0	804.0	804.0	804.0	804.0	804.0	803.7	803.3
152.5°	827.7	828.5	829.4	829.8	829.6	829.3	829.0	828.6	828.3	828.1	827.9
155°	852.0	853.1	854.3	854.9	854.6	853.9	853.2	852.5	851.8	851.6	851.5
157.5°	873.6	874.6	875.6	876.1	875.8	875.1	874.4	873.8	873.1	872.9	872.7
160°	894.2	894.9	895.6	895.9	895.5	894.6	893.8	892.9	892.1	892.1	892.1
162.5°	911.2	912.3	913.5	914.1	913.7	912.8	912.0	911.1	910.3	910.1	909.9
165°	926.4	927.5	928.7	929.3	928.8	927.8	926.7	925.7	924.7	924.7	924.7
167.5°	939.6	940.7	941.7	942.2	941.7	940.7	939.6	938.6	937.6	937.4	937.3
170°	949.9	951.0	952.2	952.8	952.2	951.0	949.9	948.7	947.5	947.5	947.5
172.5°	957.5	958.6	959.8	960.4	959.9	958.9	957.9	956.9	955.9	955.9	955.9
175°	962.8	963.9	965.1	965.7	965.2	964.2	963.2	962.2	961.2	961.2	961.2
177.5°	965.8	967.0	968.2	968.8	968.3	967.3	966.2	965.2	964.2	964.2	964.2
180°	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9
2.5°	917.0	913.2	909.4	909.4	901.1	893.5	889.7	891.2	886.7	880.6	874.5
5°	957.2	942.1	939.0	930.7	919.3	903.4	895.0	887.4	878.3	866.2	854.8
7.5°	994.4	974.7	964.0	955.7	933.7	911.7	893.5	881.4	865.4	847.2	833.6
10°	1042.9	1006.5	995.1	976.2	945.1	914.0	892.8	873.0	851.0	829.8	811.6
12.5°	1081.6	1039.9	1018.7	999.7	959.5	920.1	884.4	860.1	833.6	810.1	786.6
15°	1125.6	1078.6	1041.4	1018.7	967.8	920.1	879.9	845.7	816.1	787.3	766.8
17.5°	1146.8	1087.7	1071.0	1038.4	964.8	917.0	867.7	831.3	795.7	762.3	738.0
20°	1180.2	1111.2	1069.5	1047.5	982.3	911.7	854.1	812.3	775.2	739.5	713.7
22.5°	1182.5	1107.4	1080.1	1038.4	958.0	895.8	841.9	791.1	747.9	714.5	688.0
25°	1177.2	1100.6	1062.7	1029.3	962.5	886.7	817.7	767.6	725.1	686.4	655.3
27.5°	1174.9	1080.9	1045.2	1011.8	936.7	860.1	803.2	746.4	697.8	663.7	631.8
30°	1171.9	1059.6	1016.4	977.7	908.7	839.7	771.4	722.1	675.8	632.6	600.7
32.5°	1152.2	1030.8	986.8	945.8	871.5	802.5	748.6	696.3	646.2	606.0	577.2
35°	1146.1	1004.2	946.6	902.6	829.8	768.4	711.5	668.2	621.2	581.0	546.9
37.5°	1128.6	976.9	914.7	858.6	782.8	724.4	682.6	639.4	593.9	550.7	523.4
40°	1098.3	945.1	874.5	816.9	738.8	679.6	640.9	609.1	564.3	525.6	492.3
42.5°	1053.6	912.5	836.6	775.9	689.5	634.1	602.2	571.9	534.0	493.8	466.5
45°	1002.0	869.2	798.7	731.2	643.2	589.4	556.0	537.8	502.9	468.8	436.9
47.5°	931.4	824.5	754.7	684.9	595.4	543.1	516.5	498.3	474.1	436.9	411.1
50°	842.7	766.8	700.9	638.7	548.4	498.3	471.8	458.1	437.7	411.1	386.1
52.5°	744.1	700.1	645.5	587.8	500.6	453.6	429.3	418.7	403.5	378.5	357.3
55°	644.7	625.8	588.6	531.7	450.5	411.9	390.6	377.0	365.6	347.4	329.2
57.5°	556.0	546.9	521.1	477.1	408.8	368.6	350.4	341.3	332.2	318.6	300.4
60°	464.2	474.1	447.5	425.5	363.3	328.4	312.5	302.6	298.1	286.0	274.6
62.5°	384.6	393.7	378.5	361.8	317.8	286.7	276.9	267.7	264.7	254.1	242.7
65°	312.5	323.9	312.5	303.4	276.9	251.1	238.9	234.4	231.3	224.5	215.4
67.5°	248.8	260.2	254.9	243.5	235.1	213.9	207.1	202.5	201.0	195.7	188.1
70°	187.3	203.3	204.8	198.0	190.4	180.5	176.0	174.5	170.7	166.1	161.6
72.5°	135.0	153.2	154.0	154.0	149.4	149.4	144.9	142.6	142.6	138.0	132.7
75°	99.4	111.5	113.0	114.5	116.8	119.1	116.0	116.0	115.3	110.7	108.5
77.5°	66.0	76.6	80.4	85.7	88.7	88.7	90.3	91.8	90.3	88.0	86.5
80°	42.5	50.1	54.6	57.6	62.2	64.5	66.7	67.5	66.0	65.2	63.0
82.5°	28.1	30.3	32.6	36.4	41.7	45.5	45.5	44.8	46.3	45.5	44.8
85°	15.9	17.4	18.2	19.0	22.0	25.8	26.5	27.3	28.8	27.3	25.8
87.5°	6.1	6.8	6.8	6.8	8.3	9.1	11.4	14.4	13.7	12.1	12.1
90°	11.7	9.5	8.4	7.6	5.9	4.2	2.5	0.8	2.5	4.2	5.9
92.5°	28.8	27.8	27.3	26.8	25.8	24.8	23.8	22.8	23.8	24.8	25.8
95°	52.1	50.8	50.1	49.5	48.3	47.2	46.0	44.8	46.0	47.2	48.3
97.5°	78.9	77.9	77.4	77.0	76.1	75.3	74.4	73.6	74.4	75.3	76.1
100°	109.1	108.2	107.8	107.3	106.3	105.3	104.3	103.3	104.3	105.3	106.3
102.5°	141.5	140.3	139.7	139.4	138.9	138.4	137.9	137.4	137.9	138.4	138.9
105°	174.6	173.1	172.3	172.1	171.8	171.5	171.1	170.8	171.1	171.5	171.8
107.5°	212.1	211.4	211.1	211.0	210.8	210.7	210.5	210.3	210.5	210.7	210.8
110°	248.8	248.5	248.3	248.1	247.8	247.4	247.1	246.7	247.1	247.4	247.8

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	285.5	285.5	285.5	285.4	285.2	285.1	284.9	284.7	284.9	285.1	285.2
115°	324.4	324.7	324.9	324.7	324.2	323.7	323.2	322.7	323.2	323.7	324.2
117.5°	361.6	361.9	362.1	362.0	361.9	361.7	361.6	361.4	361.6	361.7	361.9
120°	400.3	401.2	401.6	401.1	400.1	399.1	398.1	397.1	398.1	399.1	400.1
122.5°	436.8	437.1	437.3	437.0	436.3	435.6	435.0	434.3	435.0	435.6	436.3
125°	474.0	474.3	474.5	474.2	473.7	473.2	472.7	472.2	472.7	473.2	473.7
127.5°	511.2	511.5	511.7	511.2	510.2	509.2	508.2	507.2	508.2	509.2	510.2
130°	547.4	547.9	548.2	547.5	546.2	544.8	543.5	542.1	543.5	544.8	546.2
132.5°	582.6	582.9	583.1	582.4	581.1	579.7	578.4	577.0	578.4	579.7	581.1
135°	617.0	617.1	617.2	616.7	615.7	614.7	613.7	612.7	613.7	614.7	615.7
137.5°	649.9	649.4	649.1	648.7	647.8	647.0	646.1	645.3	646.1	647.0	647.8
140°	683.6	683.4	683.3	682.9	682.0	681.2	680.3	679.5	680.3	681.2	682.0
142.5°	714.9	714.6	714.4	714.0	713.1	712.3	711.4	710.6	711.4	712.3	713.1
145°	745.6	745.1	744.8	744.6	744.3	744.0	743.6	743.3	743.6	744.0	744.3
147.5°	775.2	774.7	774.4	774.1	773.4	772.7	772.1	771.4	772.1	772.7	773.4
150°	803.0	802.7	802.5	802.3	802.0	801.7	801.3	801.0	801.3	801.7	802.0
152.5°	827.8	827.6	827.5	827.3	826.8	826.3	825.8	825.3	825.8	826.3	826.8
155°	851.3	851.2	851.1	851.1	851.1	851.1	851.1	851.1	851.1	851.1	851.1
157.5°	872.6	872.4	872.3	872.4	872.6	872.7	872.9	873.1	872.9	872.7	872.6
160°	892.1	892.1	892.1	892.3	892.6	892.9	893.3	893.6	893.3	892.9	892.6
162.5°	909.8	909.6	909.5	909.8	910.3	910.8	911.3	911.8	911.3	910.8	910.3
165°	924.7	924.7	924.7	925.0	925.5	926.0	926.5	927.0	926.5	926.0	925.5
167.5°	937.1	937.0	936.9	937.2	937.9	938.6	939.2	939.9	939.2	938.6	937.9
170°	947.5	947.5	947.5	947.8	948.5	949.2	949.8	950.5	949.8	949.2	948.5
172.5°	955.9	955.9	955.9	956.2	956.9	957.6	958.2	958.9	958.2	957.6	956.9
175°	961.2	961.2	961.2	961.5	962.2	962.9	963.5	964.2	963.5	962.9	962.2
177.5°	964.2	964.2	964.2	964.5	965.2	965.9	966.5	967.2	966.5	965.9	965.2
180°	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9
2.5°	874.5	870.8	869.2	865.4	856.3	850.3	843.4	838.9	839.7	835.9	838.1
5°	847.2	846.5	841.2	833.6	820.7	813.9	801.7	795.7	792.6	793.4	788.8
7.5°	824.5	817.7	813.9	801.7	789.6	775.2	765.3	760.0	755.5	750.9	747.9
10°	798.7	792.6	786.6	773.7	757.0	743.3	729.7	724.4	717.5	714.5	712.2
12.5°	771.4	767.6	760.0	744.8	725.9	713.0	697.1	694.0	684.9	678.9	677.3
15°	746.4	744.1	730.4	713.0	694.0	681.1	667.5	658.4	643.2	646.2	640.9
17.5°	719.8	710.0	701.6	678.1	669.0	649.3	633.3	628.8	618.2	611.3	604.5
20°	690.2	684.2	673.5	658.4	636.4	613.6	601.5	593.9	587.8	577.2	574.2
22.5°	662.2	654.6	645.5	625.8	606.8	587.8	571.1	564.3	556.7	549.2	544.6
25°	640.2	628.8	618.9	594.7	575.7	559.8	549.2	537.8	527.2	522.6	521.1
27.5°	606.0	599.2	589.4	566.6	549.2	531.7	521.8	514.3	502.9	497.6	493.0
30°	584.0	570.4	559.0	540.8	523.4	504.4	495.3	486.2	479.4	472.5	467.2
32.5°	554.5	543.8	534.7	516.5	499.1	481.6	471.8	458.1	454.3	449.0	443.0
35°	525.6	518.8	509.0	489.2	470.3	458.1	447.5	434.6	430.1	426.3	421.0
37.5°	498.3	488.5	481.6	462.7	446.0	431.6	423.2	412.6	409.6	405.0	401.2
40°	474.8	465.0	458.1	439.2	421.7	406.6	401.2	390.6	386.1	380.8	378.5
42.5°	448.3	439.9	430.8	417.2	399.0	383.8	373.2	367.1	361.0	358.8	354.2
45°	420.2	412.6	405.8	390.6	371.7	361.0	351.9	343.6	339.0	335.3	332.2
47.5°	395.9	389.1	380.0	363.3	348.1	338.3	329.2	320.8	316.3	311.7	307.9
50°	367.9	364.1	354.2	338.3	323.9	312.5	304.2	296.6	293.5	288.2	282.2
52.5°	342.8	336.0	327.7	314.8	301.9	288.2	276.9	272.3	267.0	264.0	258.6
55°	313.3	308.7	299.6	288.2	274.6	263.2	254.9	248.8	242.0	238.9	232.1
57.5°	288.2	279.9	275.3	260.9	248.0	236.7	230.6	224.5	216.9	212.4	209.3
60°	260.9	253.3	246.5	234.4	225.3	213.1	204.0	198.7	193.4	187.3	184.3
62.5°	234.4	228.3	220.0	210.1	198.7	188.9	182.0	174.5	171.4	165.4	163.1
65°	205.6	201.0	194.2	182.8	173.7	165.4	158.5	152.5	149.4	147.1	145.6
67.5°	179.8	173.7	169.1	159.3	149.4	142.6	138.8	135.0	131.2	128.9	126.7
70°	153.2	148.7	144.1	135.0	128.2	122.1	119.1	116.0	113.8	111.5	109.2
72.5°	125.9	123.6	119.1	113.0	107.7	103.2	100.9	97.1	94.8	91.0	89.5
75°	103.9	100.1	97.8	92.5	88.0	84.2	81.2	76.6	73.6	72.1	71.3
77.5°	81.9	80.4	77.4	72.8	70.5	66.7	62.2	60.7	59.2	59.2	58.4
80°	61.4	59.2	56.9	53.1	50.8	47.8	47.8	47.8	47.0	47.8	47.0
82.5°	41.7	40.2	38.7	36.4	35.6	35.6	36.4	36.4	36.4	36.4	36.4
85°	24.3	24.3	24.3	25.0	24.3	24.3	25.0	25.8	25.0	25.0	24.3
87.5°	11.4	11.4	12.1	12.1	12.9	12.9	12.9	12.9	12.9	12.9	13.7
90°	7.6	8.4	9.5	11.7	13.8	16.0	18.2	18.9	19.6	20.3	21.0
92.5°	26.8	27.3	27.8	28.8	29.9	30.9	31.9	32.4	32.9	33.4	33.9
95°	49.5	50.1	50.8	52.1	53.5	54.8	56.2	56.9	57.5	58.2	58.9
97.5°	77.0	77.4	77.9	78.9	80.0	81.0	82.0	82.8	83.7	84.5	85.4
100°	107.3	107.8	108.2	109.1	109.9	110.8	111.6	112.1	112.6	113.1	113.6
102.5°	139.4	139.7	140.3	141.5	142.6	143.8	145.0	145.5	146.0	146.5	147.0
105°	172.1	172.3	173.1	174.6	176.1	177.7	179.2	179.2	179.2	179.2	179.2
107.5°	211.0	211.1	211.4	212.1	212.8	213.4	214.1	214.6	215.1	215.6	216.1
110°	248.1	248.3	248.5	248.8	249.1	249.5	249.8	250.5	251.1	251.8	252.5

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	285.4	285.5	285.5	285.5	285.5	285.5	285.5	286.3	287.2	288.0	288.9
115°	324.7	324.9	324.7	324.4	324.1	323.7	323.4	323.6	323.8	323.9	324.1
117.5°	362.0	362.1	361.9	361.6	361.3	360.9	360.6	360.6	360.6	360.6	360.6
120°	401.1	401.6	401.2	400.3	399.5	398.6	397.8	397.6	397.5	397.3	397.2
122.5°	437.0	437.3	437.1	436.8	436.5	436.1	435.8	435.3	434.8	434.3	433.8
125°	474.2	474.5	474.3	474.0	473.7	473.3	473.0	472.3	471.7	471.0	470.3
127.5°	511.2	511.7	511.5	511.2	510.9	510.5	510.2	509.2	508.2	507.1	506.1
130°	547.5	548.2	547.9	547.4	546.9	546.4	545.9	545.2	544.5	543.8	543.1
132.5°	582.4	583.1	582.9	582.6	582.3	581.9	581.6	580.8	579.9	579.1	578.2
135°	616.7	617.2	617.1	617.0	616.8	616.7	616.5	615.8	615.1	614.4	613.7
137.5°	648.7	649.1	649.4	649.9	650.4	650.9	651.4	650.6	649.7	648.9	648.0
140°	682.9	683.3	683.4	683.6	683.7	683.9	684.1	683.9	683.7	683.6	683.4
142.5°	714.0	714.4	714.6	714.9	715.2	715.6	715.9	715.7	715.6	715.4	715.3
145°	744.6	744.8	745.1	745.6	746.1	746.6	747.1	746.9	746.7	746.6	746.4
147.5°	774.1	774.4	774.7	775.2	775.7	776.2	776.7	776.7	776.7	776.7	776.7
150°	802.3	802.5	802.7	803.0	803.3	803.7	804.0	804.0	804.0	804.0	804.0
152.5°	827.3	827.5	827.6	827.8	827.9	828.1	828.3	828.6	829.0	829.3	829.6
155°	851.1	851.1	851.2	851.3	851.5	851.6	851.8	852.5	853.2	853.9	854.6
157.5°	872.4	872.3	872.4	872.6	872.7	872.9	873.1	873.8	874.4	875.1	875.8
160°	892.3	892.1	892.1	892.1	892.1	892.1	892.1	892.9	893.8	894.6	895.5
162.5°	909.8	909.5	909.6	909.8	909.9	910.1	910.3	911.1	912.0	912.8	913.7
165°	925.0	924.7	924.7	924.7	924.7	924.7	924.7	925.7	926.7	927.8	928.8
167.5°	937.2	936.9	937.0	937.1	937.3	937.4	937.6	938.6	939.6	940.7	941.7
170°	947.8	947.5	947.5	947.5	947.5	947.5	947.5	948.7	949.9	951.0	952.2
172.5°	956.2	955.9	955.9	955.9	955.9	955.9	955.9	956.9	957.9	958.9	959.9
175°	961.5	961.2	961.2	961.2	961.2	961.2	961.2	962.2	963.2	964.2	965.2
177.5°	964.5	964.2	964.2	964.2	964.2	964.2	964.2	965.2	966.2	967.3	968.3
180°	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9
2.5°	837.4	838.1	835.9	831.3	830.6	832.1	836.6	835.1	831.3	838.1	832.1
5°	791.1	787.3	785.8	787.3	782.8	780.5	785.0	782.8	785.0	785.8	788.1
7.5°	746.4	747.1	742.6	743.3	737.3	738.8	738.8	738.8	741.1	742.6	745.6
10°	707.7	709.2	703.9	704.6	700.1	697.1	699.3	703.9	703.9	703.9	705.4
12.5°	676.6	669.8	666.0	665.2	659.9	658.4	662.9	664.4	668.2	668.2	670.5
15°	637.9	636.4	633.3	633.3	620.5	623.5	625.0	630.3	637.9	631.8	633.3
17.5°	603.0	599.2	595.4	593.9	592.4	587.8	593.9	593.1	597.7	598.5	600.7
20°	571.9	568.9	561.3	562.0	563.6	556.7	560.5	560.5	565.1	569.6	574.9
22.5°	541.6	538.5	534.7	536.3	531.7	530.2	530.2	534.0	539.3	543.1	542.3
25°	518.1	512.7	510.5	508.2	505.9	507.4	505.2	509.0	512.7	515.0	512.7
27.5°	491.5	489.2	484.7	482.4	478.6	480.1	481.6	484.7	487.0	487.0	489.2
30°	465.7	462.7	461.2	458.9	458.9	455.9	456.6	459.6	461.9	464.2	467.2
32.5°	440.7	438.4	436.1	436.1	434.6	433.9	433.1	437.7	437.7	442.2	442.2
35°	420.2	416.4	416.4	412.6	414.1	413.4	411.9	414.9	415.7	418.7	417.9
37.5°	397.5	397.5	395.9	392.1	389.1	389.9	393.7	393.7	395.9	395.2	397.5
40°	374.7	373.2	373.2	370.9	370.1	369.4	370.1	370.9	374.7	373.9	374.7
42.5°	351.9	352.7	348.9	348.9	348.9	346.6	347.4	348.1	349.7	351.2	353.5
45°	329.9	328.4	327.7	326.2	324.6	325.4	324.6	327.7	326.9	328.4	330.7
47.5°	306.4	304.2	303.4	300.4	300.4	301.9	301.1	303.4	304.2	306.4	304.9
50°	283.7	280.6	278.4	279.1	274.6	276.1	276.1	278.4	280.6	281.4	282.9
52.5°	257.1	256.4	255.6	251.8	251.1	250.3	251.1	251.8	254.9	257.1	257.9
55°	231.3	230.6	226.0	224.5	222.2	222.2	223.8	224.5	229.8	230.6	233.6
57.5°	207.8	205.6	200.2	199.5	199.5	199.5	197.2	200.2	201.8	205.6	205.6
60°	182.0	182.0	177.5	177.5	178.2	177.5	177.5	178.2	178.2	181.3	182.8
62.5°	161.6	160.8	160.8	159.3	158.5	159.3	158.5	158.5	159.3	161.6	163.8
65°	143.4	142.6	141.8	141.1	139.6	139.6	140.3	141.8	141.8	143.4	144.1
67.5°	125.9	125.9	124.4	124.4	123.6	122.9	123.6	122.9	125.9	125.9	126.7
70°	108.5	107.7	105.4	104.7	102.4	103.2	103.2	105.4	106.2	107.7	109.2
72.5°	87.2	87.2	85.7	84.2	85.0	83.4	83.4	84.2	84.2	86.5	87.2
75°	72.1	70.5	69.8	70.5	69.8	71.3	69.8	69.8	71.3	71.3	71.3
77.5°	59.2	59.2	58.4	58.4	59.2	58.4	59.2	59.2	59.2	58.4	59.2
80°	48.5	47.8	47.8	47.8	47.0	47.0	47.0	47.0	47.0	47.0	47.0
82.5°	36.4	36.4	35.6	36.4	36.4	35.6	36.4	35.6	35.6	36.4	36.4
85°	24.3	25.8	24.3	24.3	25.0	25.0	25.8	25.0	25.8	24.3	25.0
87.5°	12.9	13.7	13.7	12.9	12.9	13.7	13.7	13.7	14.4	12.9	13.7
90°	21.3	21.5	21.8	22.1	22.5	22.8	22.5	22.1	21.8	21.5	21.3
92.5°	34.2	34.0	33.7	33.3	33.0	32.6	33.0	33.3	33.7	34.0	34.2
95°	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2
97.5°	85.8	85.7	85.5	85.4	85.2	85.0	85.2	85.4	85.5	85.7	85.8
100°	113.9	114.1	114.4	114.7	115.1	115.4	115.1	114.7	114.4	114.1	113.9
102.5°	147.3	147.2	147.0	146.9	146.7	146.5	146.7	146.9	147.0	147.2	147.3
105°	179.2	179.4	179.7	180.0	180.4	180.7	180.4	180.0	179.7	179.4	179.2
107.5°	216.4	216.3	216.1	216.0	215.8	215.6	215.8	216.0	216.1	216.3	216.4
110°	252.8	252.6	252.3	252.0	251.6	251.3	251.6	252.0	252.3	252.6	252.8

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	289.3	289.3	289.3	289.3	289.3	289.3	289.3	289.3	289.3	289.3	289.3
115°	324.2	324.1	323.9	323.8	323.6	323.4	323.6	323.8	323.9	324.1	324.2
117.5°	360.6	360.4	359.9	359.4	358.9	358.4	358.9	359.4	359.9	360.4	360.6
120°	397.1	396.9	396.6	396.3	395.9	395.6	395.9	396.3	396.6	396.9	397.1
122.5°	433.5	433.2	432.7	432.2	431.7	431.2	431.7	432.2	432.7	433.2	433.5
125°	470.0	469.7	469.0	468.3	467.6	466.9	467.6	468.3	469.0	469.7	470.0
127.5°	505.6	505.3	504.6	503.9	503.3	502.6	503.3	503.9	504.6	505.3	505.6
130°	542.8	542.2	541.0	539.9	538.7	537.5	538.7	539.9	541.0	542.2	542.8
132.5°	577.8	577.4	576.5	575.7	574.8	574.0	574.8	575.7	576.5	577.4	577.8
135°	613.4	613.2	612.9	612.6	612.2	611.9	612.2	612.6	612.9	613.2	613.4
137.5°	647.6	647.3	646.8	646.3	645.8	645.3	645.8	646.3	646.8	647.3	647.6
140°	683.3	682.7	681.5	680.4	679.2	678.0	679.2	680.4	681.5	682.7	683.3
142.5°	715.2	714.8	713.9	713.1	712.2	711.4	712.2	713.1	713.9	714.8	715.2
145°	746.3	746.0	745.3	744.6	744.0	743.3	744.0	744.6	745.3	746.0	746.3
147.5°	776.7	776.2	775.2	774.1	773.1	772.1	773.1	774.1	775.2	776.2	776.7
150°	804.0	803.5	802.5	801.5	800.5	799.5	800.5	801.5	802.5	803.5	804.0
152.5°	829.8	829.4	828.5	827.7	826.8	826.0	826.8	827.7	828.5	829.4	829.8
155°	854.9	854.3	853.1	852.0	850.8	849.6	850.8	852.0	853.1	854.3	854.9
157.5°	876.1	875.6	874.6	873.6	872.6	871.6	872.6	873.6	874.6	875.6	876.1
160°	895.9	895.6	894.9	894.2	893.5	892.8	893.5	894.2	894.9	895.6	895.9
162.5°	914.1	913.5	912.3	911.2	910.0	908.8	910.0	911.2	912.3	913.5	914.1
165°	929.3	928.7	927.5	926.4	925.2	924.0	925.2	926.4	927.5	928.7	929.3
167.5°	942.2	941.7	940.7	939.6	938.6	937.6	938.6	939.6	940.7	941.7	942.2
170°	952.8	952.2	951.0	949.9	948.7	947.5	948.7	949.9	951.0	952.2	952.8
172.5°	960.4	959.8	958.6	957.5	956.3	955.1	956.3	957.5	958.6	959.8	960.4
175°	965.7	965.1	963.9	962.8	961.6	960.4	961.6	962.8	963.9	965.1	965.7
177.5°	968.8	968.2	967.0	965.8	964.6	963.4	964.6	965.8	967.0	968.2	968.8
180°	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9	885.9
2.5°	838.1	841.2	838.1	832.1	838.1	841.9	845.7	851.8	854.8	854.8	859.4
5°	790.4	796.4	794.1	792.6	798.7	802.5	808.6	816.1	824.5	829.8	835.9
7.5°	747.9	751.7	755.5	755.5	761.5	769.9	779.0	788.1	798.7	806.3	810.8
10°	710.7	713.7	716.0	719.1	728.2	737.3	749.4	760.8	769.9	778.2	785.8
12.5°	675.1	679.6	684.9	687.2	694.0	705.4	716.8	730.4	744.8	753.2	760.8
15°	640.9	643.2	649.3	656.1	662.2	674.3	688.7	703.1	715.3	728.2	735.0
17.5°	606.0	606.8	622.7	618.9	638.7	650.0	657.6	671.3	691.0	701.6	712.2
20°	571.9	579.5	586.3	590.1	600.7	613.6	635.6	646.2	662.2	672.0	681.1
22.5°	545.4	556.7	556.7	565.8	571.1	583.3	599.2	619.7	637.1	644.0	656.9
25°	521.8	527.2	536.3	539.3	549.2	559.8	570.4	592.4	611.3	620.5	629.6
27.5°	491.5	498.3	510.5	510.5	523.4	534.7	547.6	562.0	581.0	593.9	603.8
30°	468.0	474.8	480.1	488.5	493.8	504.4	527.2	537.8	554.5	565.8	578.0
32.5°	446.0	451.3	455.9	465.0	471.0	483.2	495.3	514.3	528.7	539.3	552.2
35°	421.7	427.0	433.1	439.9	449.0	460.4	471.8	487.7	502.1	512.0	522.6
37.5°	399.0	402.8	411.9	416.4	424.0	434.6	449.0	465.7	478.6	486.2	496.8
40°	377.0	380.0	386.8	395.2	400.5	408.8	424.0	438.4	454.3	463.4	471.8
42.5°	353.5	357.3	363.3	371.7	380.0	389.1	397.5	414.1	428.6	436.1	445.2
45°	333.0	335.3	339.8	348.1	356.5	363.3	376.2	391.4	405.0	411.1	421.0
47.5°	308.7	311.0	317.8	321.6	330.7	339.8	352.7	367.9	380.0	386.1	395.2
50°	283.7	286.0	290.5	298.8	304.9	314.8	326.2	339.0	354.2	362.6	367.9
52.5°	259.4	264.0	267.7	274.6	282.2	292.0	302.6	314.8	327.7	336.0	342.1
55°	235.1	238.9	243.5	247.3	256.4	265.5	277.6	289.0	300.4	307.9	314.8
57.5°	207.8	213.1	217.7	225.3	232.1	239.7	253.3	262.4	276.1	281.4	287.5
60°	184.3	189.6	193.4	199.5	205.6	215.4	224.5	235.9	247.3	254.1	261.7
62.5°	164.6	166.9	169.1	175.2	181.3	190.4	199.5	210.9	223.0	226.8	232.9
65°	144.9	147.1	150.9	156.3	160.8	166.1	176.0	185.1	196.5	202.5	204.8
67.5°	128.2	130.5	131.2	135.0	138.8	144.9	150.2	159.3	169.9	173.7	178.2
70°	109.2	113.0	113.8	116.8	118.3	122.1	128.2	135.0	143.4	150.2	154.0
72.5°	87.2	92.5	94.1	98.6	100.9	104.7	109.2	114.5	119.8	122.9	125.9
75°	71.3	72.8	73.6	77.4	81.2	86.5	88.7	91.8	96.3	100.1	103.2
77.5°	59.2	59.9	60.7	60.7	61.4	64.5	69.0	72.8	75.8	77.4	79.6
80°	47.8	47.0	47.0	47.8	47.8	47.8	49.3	54.6	56.1	59.9	59.2
82.5°	37.2	35.6	36.4	35.6	35.6	35.6	35.6	36.4	36.4	38.7	40.2
85°	24.3	25.0	24.3	24.3	23.5	24.3	23.5	23.5	22.8	22.8	22.0
87.5°	12.9	13.7	12.9	12.9	12.1	12.9	12.1	12.1	11.4	11.4	9.9
90°	21.0	20.3	19.6	18.9	18.2	16.0	13.8	11.7	9.5	8.4	7.6
92.5°	33.9	33.4	32.9	32.4	31.9	30.9	29.9	28.8	27.8	27.3	26.8
95°	58.9	58.2	57.5	56.9	56.2	54.8	53.5	52.1	50.8	50.1	49.5
97.5°	85.4	84.5	83.7	82.8	82.0	81.0	80.0	78.9	77.9	77.4	77.0
100°	113.6	113.1	112.6	112.1	111.6	110.8	109.9	109.1	108.2	107.8	107.3
102.5°	147.0	146.5	146.0	145.5	145.0	143.8	142.6	141.5	140.3	139.7	139.4
105°	179.2	179.2	179.2	179.2	179.2	177.7	176.1	174.6	173.1	172.3	172.1
107.5°	216.1	215.6	215.1	214.6	214.1	213.4	212.8	212.1	211.4	211.1	211.0
110°	252.5	251.8	251.1	250.5	249.8	249.5	249.1	248.8	248.5	248.3	248.1

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	288.9	288.0	287.2	286.3	285.5	285.5	285.5	285.5	285.5	285.5	285.4
115°	324.1	323.9	323.8	323.6	323.4	323.7	324.1	324.4	324.7	324.9	324.7
117.5°	360.6	360.6	360.6	360.6	360.6	360.9	361.3	361.6	361.9	362.1	362.0
120°	397.2	397.3	397.5	397.6	397.8	398.6	399.5	400.3	401.2	401.6	401.1
122.5°	433.8	434.3	434.8	435.3	435.8	436.1	436.5	436.8	437.1	437.3	437.0
125°	470.3	471.0	471.7	472.3	473.0	473.3	473.7	474.0	474.3	474.5	474.2
127.5°	506.1	507.1	508.2	509.2	510.2	510.5	510.9	511.2	511.5	511.7	511.2
130°	543.1	543.8	544.5	545.2	545.9	546.4	546.9	547.4	547.9	548.2	547.5
132.5°	578.2	579.1	579.9	580.8	581.6	581.9	582.3	582.6	582.9	583.1	582.4
135°	613.7	614.4	615.1	615.8	616.5	616.7	616.8	617.0	617.1	617.2	616.7
137.5°	648.0	648.9	649.7	650.6	651.4	650.9	650.4	649.9	649.4	649.1	648.7
140°	683.4	683.6	683.7	683.9	684.1	683.9	683.7	683.6	683.4	683.3	682.9
142.5°	715.3	715.4	715.6	715.7	715.9	715.6	715.2	714.9	714.6	714.4	714.0
145°	746.4	746.6	746.7	746.9	747.1	746.6	746.1	745.6	745.1	744.8	744.6
147.5°	776.7	776.7	776.7	776.7	776.7	776.2	775.7	775.2	774.7	774.4	774.1
150°	804.0	804.0	804.0	804.0	804.0	803.7	803.3	803.0	802.7	802.5	802.3
152.5°	829.6	829.3	829.0	828.6	828.3	828.1	827.9	827.8	827.6	827.5	827.3
155°	854.6	853.9	853.2	852.5	851.8	851.6	851.5	851.3	851.2	851.1	851.1
157.5°	875.8	875.1	874.4	873.8	873.1	872.9	872.7	872.6	872.4	872.3	872.4
160°	895.5	894.6	893.8	892.9	892.1	892.1	892.1	892.1	892.1	892.1	892.3
162.5°	913.7	912.8	912.0	911.1	910.3	910.1	909.9	909.8	909.6	909.5	909.8
165°	928.8	927.8	926.7	925.7	924.7	924.7	924.7	924.7	924.7	924.7	925.0
167.5°	941.7	940.7	939.6	938.6	937.6	937.4	937.3	937.1	937.0	936.9	937.2
170°	952.2	951.0	949.9	948.7	947.5	947.5	947.5	947.5	947.5	947.5	947.8
172.5°	959.9	958.9	957.9	956.9	955.9	955.9	955.9	955.9	955.9	955.9	956.2
175°	965.2	964.2	963.2	962.2	961.2	961.2	961.2	961.2	961.2	961.2	961.5
177.5°	968.3	967.3	966.2	965.2	964.2	964.2	964.2	964.2	964.2	964.2	964.5
180°	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5	966.5

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	885.9	885.9	885.9	885.9
2.5°	863.2	868.5	879.1	888.2
5°	845.0	853.3	869.2	885.2
7.5°	823.0	835.9	856.3	878.3
10°	801.7	818.4	843.4	869.2
12.5°	780.5	797.9	824.5	857.9
15°	755.5	773.7	805.5	845.7
17.5°	733.5	757.7	786.6	826.8
20°	710.0	728.2	765.3	807.8
22.5°	680.4	710.7	745.6	790.4
25°	656.9	683.4	718.3	769.1
27.5°	628.0	659.1	701.6	746.4
30°	604.5	630.3	669.8	723.6
32.5°	577.2	607.6	648.5	701.6
35°	552.9	578.7	617.4	671.3
37.5°	524.1	552.2	595.4	643.2
40°	499.1	526.4	567.4	612.1
42.5°	468.8	497.6	538.5	576.5
45°	444.5	471.0	503.6	538.5
47.5°	414.9	443.0	474.8	499.1
50°	388.4	414.1	439.2	459.6
52.5°	359.5	383.0	405.8	421.0
55°	333.0	351.2	369.4	380.0
57.5°	301.9	319.3	334.5	340.6
60°	274.6	289.0	298.8	305.7
62.5°	245.8	256.4	264.0	267.7
65°	217.7	225.3	229.1	232.9
67.5°	188.9	195.7	198.0	202.5
70°	158.5	166.1	167.6	169.9
72.5°	135.8	135.8	138.8	141.8
75°	108.5	110.0	111.5	111.5
77.5°	85.0	85.0	86.5	87.2
80°	62.2	63.0	63.0	62.2
82.5°	42.5	44.0	42.5	41.7
85°	23.5	26.5	25.0	25.0
87.5°	9.9	9.9	11.4	9.9
90°	5.9	4.2	2.5	0.8
92.5°	25.8	24.8	23.8	22.8
95°	48.3	47.2	46.0	44.8
97.5°	76.1	75.3	74.4	73.6
100°	106.3	105.3	104.3	103.3
102.5°	138.9	138.4	137.9	137.4
105°	171.8	171.5	171.1	170.8
107.5°	210.8	210.7	210.5	210.3
110°	247.8	247.4	247.1	246.7

TEST NUMBER: P1012687

CATALOG NUMBER: S123RDIP-B560D805UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	285.2	285.1	284.9	284.7
115°	324.2	323.7	323.2	322.7
117.5°	361.9	361.7	361.6	361.4
120°	400.1	399.1	398.1	397.1
122.5°	436.3	435.6	435.0	434.3
125°	473.7	473.2	472.7	472.2
127.5°	510.2	509.2	508.2	507.2
130°	546.2	544.8	543.5	542.1
132.5°	581.1	579.7	578.4	577.0
135°	615.7	614.7	613.7	612.7
137.5°	647.8	647.0	646.1	645.3
140°	682.0	681.2	680.3	679.5
142.5°	713.1	712.3	711.4	710.6
145°	744.3	744.0	743.6	743.3
147.5°	773.4	772.7	772.1	771.4
150°	802.0	801.7	801.3	801.0
152.5°	826.8	826.3	825.8	825.3
155°	851.1	851.1	851.1	851.1
157.5°	872.6	872.7	872.9	873.1
160°	892.6	892.9	893.3	893.6
162.5°	910.3	910.8	911.3	911.8
165°	925.5	926.0	926.5	927.0
167.5°	937.9	938.6	939.2	939.9
170°	948.5	949.2	949.8	950.5
172.5°	956.9	957.6	958.2	958.9
175°	962.2	962.9	963.5	964.2
177.5°	965.2	965.9	966.5	967.2
180°	966.5	966.5	966.5	966.5

(END OF REPORT)