

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012699

Luminaire Tested: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012699
REPORT IS A COMBINATION OF REPORTS P993520 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6493.0 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47		47
1	98	94	90	87	90	86	83	80	72	70	68	60	58	57	48	47	46	41		41
2	89	82	76	72	82	76	71	67	64	60	57	53	50	48	43	41	40	35		35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30		30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26		26
5	69	58	50	44	63	54	47	42	46	41	37	38	34	31	31	29	26	23		23
6	64	52	44	39	59	48	41	36	41	36	32	35	31	28	29	26	24	21		21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18		18
8	55	43	35	30	50	40	33	29	34	29	25	29	25	22	24	21	19	17		17
9	51	39	32	27	47	37	30	26	32	26	23	27	23	20	22	19	17	15		15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14		14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13119	13119	13119	13119
5°	13130	15110	13163	11210
10°	13014	18240	13070	9791
15°	12879	20701	12879	8634
20°	12616	22330	12686	7659
25°	12422	21214	12398	6988
30°	12197	14699	12171	6333
35°	11926	9438	11873	5838
40°	11589	6664	11533	5346
45°	11003	5333	10988	4868
50°	10284	4461	10249	4307
55°	9473	3676	9397	3652
60°	8677	3039	8592	3106
65°	7745	2432	7796	2632
70°	6885	1690	7068	2128
75°	5835	1253	6075	1637
80°	4647	831	5044	1227
85°	3304	392	3612	762

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 17515 cd/sqm

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.7	1.8
10°-20°	374.7	5.8
20°-30°	590.1	9.1
30°-40°	613.6	9.5
40°-50°	525.0	8.1
50°-60°	400.3	6.2
60°-70°	256.4	3.9
70°-80°	122.9	1.9
80°-90°	34.9	0.5
90°-100°	80.3	1.2
100°-110°	243.0	3.7
110°-120°	413.6	6.4
120°-130°	544.2	8.4
130°-140°	611.7	9.4
140°-150°	601.3	9.3
150°-160°	506.3	7.8
160°-170°	337.0	5.2
170°-180°	118.0	1.8
0°-30°	1084.5	16.7
0°-40°	1698.2	26.2
0°-60°	2623.4	40.4
0°-90°	3037.6	46.8
90°-120°	736.9	11.3
90°-150°	2494.0	38.4
90°-180°	3455.0	53.2
0°-180°	6493.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1219	1219	1219	1219	1219	
5°	1218	1447	1221	1074	1218	116
15°	1164	2057	1164	858	1164	327
25°	1058	2119	1056	698	1058	487
35°	924	919	919	569	924	578
45°	741	490	740	448	741	570
55°	523	308	519	306	523	468
65°	320	177	322	192	320	320
75°	153	75	160	98	153	166
85°	34	18	38	34	34	38
90°	1	29	1	29	1	6
95°	58	76	58	76	58	64
105°	220	233	220	233	220	236
115°	416	417	416	417	416	412
125°	609	602	609	602	609	543
135°	791	790	791	790	791	609
145°	959	959	959	959	959	599
155°	1098	1096	1098	1096	1098	506
165°	1196	1192	1196	1192	1196	337
175°	1244	1239	1244	1239	1244	118
180°	1247	1247	1247	1247	1247	

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1222.0	1230.3	1236.6	1240.8	1251.2	1257.5	1262.7	1272.1	1272.1	1274.2	1278.3
5°	1217.8	1235.5	1248.1	1264.8	1286.7	1297.1	1311.7	1324.2	1342.0	1351.4	1360.8
7.5°	1208.4	1233.5	1259.5	1284.6	1316.9	1337.8	1352.4	1384.8	1407.7	1435.9	1457.8
10°	1195.9	1230.3	1263.7	1302.3	1346.2	1377.5	1399.4	1442.2	1486.0	1525.6	1559.0
12.5°	1180.2	1222.0	1270.0	1316.9	1378.5	1409.8	1445.3	1498.5	1561.1	1611.2	1656.1
15°	1163.5	1211.5	1265.8	1323.2	1400.4	1444.3	1495.4	1560.1	1630.0	1702.0	1763.6
17.5°	1137.5	1198.0	1258.5	1342.0	1432.8	1458.9	1502.7	1591.4	1678.0	1742.7	1817.8
20°	1111.4	1179.2	1255.4	1330.5	1428.6	1489.1	1529.8	1623.7	1716.6	1794.9	1866.9
22.5°	1087.4	1158.3	1237.6	1332.6	1424.4	1484.9	1536.1	1634.2	1741.7	1829.3	1918.0
25°	1058.1	1135.4	1223.0	1312.8	1424.4	1470.3	1526.7	1640.4	1754.2	1855.4	1965.0
27.5°	1026.8	1105.1	1191.7	1283.5	1385.8	1453.6	1509.0	1631.0	1769.8	1878.4	1991.1
30°	995.5	1075.9	1159.4	1241.8	1356.6	1421.3	1484.9	1619.6	1778.2	1902.4	1989.0
32.5°	965.3	1033.1	1115.5	1195.9	1309.6	1380.6	1452.6	1608.1	1781.3	1885.7	1927.4
35°	923.5	994.5	1061.3	1146.8	1261.6	1331.6	1416.1	1607.0	1767.7	1832.4	1811.6
37.5°	884.9	944.4	1008.1	1084.2	1202.2	1292.9	1380.6	1579.9	1722.9	1727.0	1609.1
40°	842.1	891.2	944.4	1024.8	1152.1	1241.8	1336.8	1538.2	1641.5	1579.9	1372.2
42.5°	793.1	836.9	878.7	956.9	1095.7	1195.9	1298.2	1486.0	1523.6	1381.6	1165.6
45°	740.9	776.4	815.0	897.4	1036.2	1135.4	1237.6	1405.6	1367.0	1166.7	961.1
47.5°	686.6	716.9	754.5	829.6	972.6	1073.8	1170.8	1290.9	1192.8	977.8	805.6
50°	632.4	656.4	692.9	770.1	907.9	999.7	1089.5	1167.7	1030.0	839.0	665.8
52.5°	579.2	597.9	635.5	701.3	834.8	922.5	987.2	1017.4	877.6	692.9	578.1
55°	522.8	543.7	568.7	635.5	768.0	832.7	875.5	874.5	730.5	587.5	477.9
57.5°	468.5	487.3	509.2	576.0	683.5	727.3	763.9	746.1	609.4	481.1	410.1
60°	420.5	431.0	455.0	511.3	592.7	630.3	651.2	620.9	497.8	405.9	339.1
62.5°	368.4	378.8	398.6	451.9	501.9	521.8	539.5	500.9	411.2	330.8	290.1
65°	320.4	333.9	346.5	389.2	416.4	440.4	438.3	405.9	321.4	269.2	235.8
67.5°	278.6	283.8	294.3	320.4	332.9	350.6	351.7	315.1	258.8	219.1	199.3
70°	233.8	239.0	246.3	258.8	267.1	271.3	269.2	236.9	195.1	171.1	153.4
72.5°	195.1	194.1	199.3	199.3	207.7	206.6	200.4	175.3	148.2	128.4	117.9
75°	153.4	154.4	155.5	153.4	150.3	146.1	140.9	122.1	104.4	95.0	85.6
77.5°	120.0	117.9	119.0	111.7	107.5	103.3	96.0	86.6	72.0	69.9	65.7
80°	85.6	84.5	83.5	80.4	71.0	66.8	61.6	56.4	53.2	51.1	50.1
82.5°	57.4	57.4	55.3	49.0	43.8	40.7	39.7	37.6	34.4	34.4	33.4
85°	34.4	33.4	31.3	25.0	21.9	21.9	21.9	21.9	19.8	19.8	18.8
87.5°	13.6	12.5	9.4	9.4	8.3	8.3	8.3	7.3	7.3	6.3	6.3
90°	1.0	3.2	5.4	7.5	9.7	10.8	12.2	15.0	17.9	20.7	23.5
92.5°	29.4	30.7	32.0	33.3	34.6	35.3	35.9	37.2	38.5	39.8	41.1
95°	57.8	59.3	60.9	62.4	63.9	64.7	65.6	67.3	69.0	70.8	72.5
97.5°	95.0	96.1	97.2	98.3	99.4	99.9	100.6	101.9	103.2	104.5	105.8
100°	133.2	134.5	135.8	137.1	138.4	139.1	139.6	140.7	141.8	142.9	144.0
102.5°	177.3	177.9	178.6	179.2	179.9	180.2	181.0	182.5	184.0	185.6	187.1
105°	220.4	220.8	221.3	221.7	222.2	222.4	223.4	225.3	227.3	229.2	231.2
107.5°	271.4	271.6	271.8	272.0	272.2	272.3	272.7	273.6	274.5	275.4	276.3
110°	318.4	318.8	319.2	319.7	320.1	320.3	320.5	321.0	321.4	321.9	322.3

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	367.4	367.6	367.8	368.0	368.2	368.3	368.3	368.3	368.3	368.3	368.3
115°	416.3	417.0	417.6	418.3	419.0	419.3	419.1	418.6	418.2	417.7	417.3
117.5°	466.3	466.5	466.7	467.0	467.2	467.3	467.1	466.6	466.2	465.7	465.3
120°	512.3	513.6	514.9	516.2	517.5	518.2	517.7	516.6	515.5	514.4	513.3
122.5°	560.3	561.2	562.1	563.0	563.9	564.3	564.1	563.6	563.2	562.7	562.3
125°	609.3	610.0	610.6	611.3	612.0	612.3	612.1	611.6	611.2	610.7	610.3
127.5°	654.4	655.7	657.0	658.3	659.6	660.3	660.1	659.6	659.2	658.7	658.3
130°	699.4	701.2	702.9	704.7	706.4	707.3	707.0	706.3	705.6	705.0	704.3
132.5°	744.5	746.2	748.0	749.7	751.4	752.3	752.1	751.7	751.2	750.8	750.4
135°	790.6	791.9	793.2	794.5	795.8	796.4	796.3	796.1	795.9	795.7	795.5
137.5°	832.7	833.8	834.9	836.0	837.1	837.6	837.9	838.6	839.2	839.9	840.5
140°	876.8	877.9	879.0	880.1	881.2	881.7	881.8	882.0	882.2	882.4	882.6
142.5°	916.9	918.0	919.1	920.2	921.3	921.8	922.0	922.5	922.9	923.4	923.8
145°	959.0	959.4	959.9	960.3	960.8	961.0	961.3	962.0	962.6	963.3	963.9
147.5°	995.3	996.2	997.0	997.9	998.8	999.2	999.5	1000.2	1000.9	1001.5	1002.2
150°	1033.5	1033.9	1034.4	1034.8	1035.3	1035.5	1035.7	1036.1	1036.6	1037.0	1037.4
152.5°	1064.8	1065.5	1066.1	1066.8	1067.5	1067.8	1067.9	1068.1	1068.4	1068.6	1068.8
155°	1098.2	1098.2	1098.2	1098.2	1098.2	1098.2	1098.3	1098.5	1098.7	1098.9	1099.1
157.5°	1126.6	1126.4	1126.2	1125.9	1125.7	1125.6	1125.7	1125.9	1126.2	1126.4	1126.6
160°	1153.0	1152.6	1152.2	1151.7	1151.3	1151.1	1151.1	1151.1	1151.1	1151.1	1151.1
162.5°	1176.5	1175.9	1175.2	1174.6	1173.9	1173.6	1173.7	1173.9	1174.2	1174.4	1174.6
165°	1196.1	1195.5	1194.8	1194.2	1193.5	1193.2	1193.2	1193.2	1193.2	1193.2	1193.2
167.5°	1212.8	1211.9	1211.1	1210.2	1209.3	1208.9	1209.0	1209.2	1209.4	1209.6	1209.8
170°	1226.5	1225.6	1224.8	1223.9	1223.0	1222.6	1222.6	1222.6	1222.6	1222.6	1222.6
172.5°	1237.3	1236.4	1235.5	1234.6	1233.7	1233.3	1233.3	1233.3	1233.3	1233.3	1233.3
175°	1244.1	1243.2	1242.4	1241.5	1240.6	1240.2	1240.2	1240.2	1240.2	1240.2	1240.2
177.5°	1248.0	1247.1	1246.3	1245.4	1244.5	1244.1	1244.1	1244.1	1244.1	1244.1	1244.1
180°	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1286.7	1286.7	1296.1	1305.5	1300.2	1303.4	1314.9	1310.7	1319.0	1318.0	1321.1
5°	1383.7	1395.2	1404.6	1424.4	1427.6	1424.4	1444.3	1449.5	1458.9	1447.4	1452.6
7.5°	1493.3	1517.3	1540.3	1569.5	1578.9	1581.0	1591.4	1606.0	1618.5	1595.6	1607.0
10°	1599.7	1636.3	1683.2	1709.3	1732.3	1740.6	1749.0	1758.4	1773.0	1786.5	1776.1
12.5°	1714.5	1767.7	1812.6	1859.6	1887.8	1884.6	1908.6	1914.9	1926.4	1929.5	1933.7
15°	1808.4	1883.6	1911.8	1981.7	1987.9	2008.8	2035.9	2059.9	2063.1	2056.8	2056.8
17.5°	1898.2	1962.9	2013.0	2069.3	2080.8	2098.5	2133.0	2144.5	2148.6	2147.6	2147.6
20°	1971.2	2014.0	2098.5	2145.5	2164.3	2187.2	2211.2	2225.9	2229.0	2233.2	2226.9
22.5°	2019.2	2083.9	2152.8	2191.4	2207.1	2215.4	2231.1	2235.3	2230.0	2231.1	2232.1
25°	2056.8	2120.5	2162.2	2172.6	2171.6	2161.2	2149.7	2129.9	2127.8	2119.4	2102.7
27.5°	2067.2	2091.2	2086.0	2043.2	2000.5	1996.3	1927.4	1889.8	1847.1	1853.3	1829.3
30°	2010.9	1979.6	1905.5	1797.0	1752.1	1679.0	1601.8	1521.5	1490.2	1455.7	1519.4
32.5°	1873.1	1761.5	1630.0	1489.1	1414.0	1349.3	1266.9	1208.4	1175.0	1146.8	1201.1
35°	1665.5	1491.2	1316.9	1183.4	1121.8	1063.4	986.1	956.9	915.2	919.4	924.6
37.5°	1398.3	1206.3	1074.8	943.4	902.7	878.7	822.3	777.4	762.8	758.6	758.6
40°	1147.9	990.3	873.4	770.1	738.8	719.0	674.1	653.3	637.6	633.4	638.6
42.5°	949.6	815.0	724.2	655.3	633.4	608.4	589.6	563.5	560.4	553.1	562.5
45°	797.3	680.4	612.6	562.5	543.7	534.3	513.4	497.8	491.5	490.5	497.8
47.5°	676.2	585.4	525.9	494.6	480.0	470.6	452.9	446.6	440.4	442.5	439.3
50°	567.7	499.9	461.2	433.1	423.7	414.3	402.8	396.5	393.4	393.4	392.4
52.5°	487.3	431.0	405.9	379.8	375.7	370.5	357.9	353.8	348.5	347.5	351.7
55°	417.4	378.8	353.8	338.1	333.9	323.5	318.3	313.1	309.9	307.8	308.9
57.5°	356.9	327.7	311.0	297.4	290.1	285.9	276.5	275.5	273.4	273.4	272.4
60°	306.8	285.9	266.1	257.8	252.5	247.3	246.3	240.0	236.9	239.0	237.9
62.5°	259.8	243.1	231.7	222.3	219.1	215.0	211.8	209.8	206.6	207.7	207.7
65°	217.1	203.5	195.1	186.8	185.7	181.6	180.5	178.4	178.4	177.4	179.5
67.5°	178.4	169.1	161.7	156.5	153.4	154.4	150.3	147.1	147.1	146.1	149.2
70°	141.9	136.7	129.4	123.1	119.0	119.0	113.7	112.7	112.7	112.7	111.7
72.5°	109.6	100.2	97.0	95.0	95.0	95.0	92.9	92.9	91.8	92.9	91.8
75°	81.4	80.4	78.3	77.2	77.2	76.2	75.1	75.1	75.1	75.1	75.1
77.5°	63.7	63.7	61.6	60.5	60.5	60.5	59.5	59.5	58.4	58.4	58.4
80°	47.0	47.0	44.9	44.9	44.9	43.8	43.8	43.8	44.9	43.8	43.8
82.5°	32.3	32.3	31.3	32.3	31.3	30.3	30.3	30.3	29.2	30.3	30.3
85°	18.8	18.8	17.7	16.7	17.7	17.7	16.7	17.7	16.7	17.7	16.7
87.5°	7.3	6.3	6.3	6.3	5.2	6.3	5.2	5.2	6.3	5.2	6.3
90°	24.4	25.2	26.1	27.0	27.4	27.6	28.1	28.5	29.0	29.4	29.0
92.5°	41.8	42.4	43.1	43.8	44.1	43.9	43.4	43.0	42.5	42.1	42.5
95°	73.4	74.2	75.1	76.0	76.4	76.4	76.4	76.4	76.4	76.4	76.4
97.5°	106.9	108.0	109.1	110.2	110.7	110.6	110.4	110.1	109.9	109.7	109.9
100°	144.6	145.3	145.9	146.6	146.9	147.1	147.6	148.0	148.5	148.9	148.5
102.5°	187.7	188.4	189.0	189.7	190.0	189.9	189.7	189.5	189.3	189.1	189.3
105°	231.2	231.2	231.2	231.2	231.2	231.4	231.8	232.3	232.7	233.1	232.7
107.5°	276.9	277.6	278.2	278.9	279.2	279.1	278.9	278.6	278.4	278.2	278.4
110°	323.2	324.0	324.9	325.8	326.2	326.0	325.6	325.1	324.7	324.3	324.7

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	369.4	370.5	371.6	372.7	373.2	373.2	373.2	373.2	373.2	373.2	373.2
115°	417.5	417.7	418.0	418.2	418.3	418.2	418.0	417.7	417.5	417.3	417.5
117.5°	465.3	465.3	465.3	465.3	465.3	465.0	464.3	463.7	463.0	462.4	463.0
120°	513.1	512.9	512.6	512.4	512.3	512.1	511.7	511.2	510.8	510.4	510.8
122.5°	561.7	561.0	560.4	559.7	559.4	559.1	558.4	557.7	557.1	556.4	557.1
125°	609.4	608.6	607.7	606.8	606.4	606.0	605.1	604.2	603.4	602.5	603.4
127.5°	657.0	655.7	654.4	653.1	652.4	652.0	651.1	650.2	649.4	648.5	649.4
130°	703.4	702.6	701.7	700.8	700.4	699.6	698.1	696.6	695.1	693.6	695.1
132.5°	749.3	748.2	747.1	746.0	745.5	745.0	743.9	742.8	741.7	740.6	741.7
135°	794.6	793.7	792.8	791.9	791.5	791.3	790.9	790.4	790.0	789.6	790.0
137.5°	839.4	838.3	837.2	836.1	835.6	835.3	834.6	834.0	833.3	832.7	833.3
140°	882.4	882.2	882.0	881.8	881.7	880.9	879.4	877.9	876.3	874.8	876.3
142.5°	923.6	923.4	923.1	922.9	922.8	922.3	921.2	920.1	919.0	917.9	919.0
145°	963.7	963.5	963.3	963.1	963.0	962.6	961.7	960.8	959.9	959.0	959.9
147.5°	1002.2	1002.2	1002.2	1002.2	1002.2	1001.5	1000.2	998.9	997.6	996.3	997.6
150°	1037.4	1037.4	1037.4	1037.4	1037.4	1036.7	1035.4	1034.1	1032.8	1031.5	1032.8
152.5°	1069.2	1069.6	1070.1	1070.5	1070.7	1070.2	1069.1	1068.0	1066.9	1065.8	1066.9
155°	1100.0	1100.9	1101.8	1102.7	1103.1	1102.3	1100.8	1099.3	1097.7	1096.2	1097.7
157.5°	1127.5	1128.3	1129.2	1130.1	1130.5	1129.8	1128.5	1127.2	1125.9	1124.6	1125.9
160°	1152.2	1153.3	1154.4	1155.5	1156.0	1155.6	1154.7	1153.8	1152.9	1152.0	1152.9
162.5°	1175.7	1176.8	1177.9	1179.0	1179.5	1178.7	1177.2	1175.7	1174.1	1172.6	1174.1
165°	1194.5	1195.8	1197.1	1198.4	1199.1	1198.3	1196.8	1195.3	1193.7	1192.2	1193.7
167.5°	1211.1	1212.4	1213.7	1215.0	1215.7	1215.0	1213.7	1212.4	1211.1	1209.8	1211.1
170°	1224.1	1225.6	1227.1	1228.6	1229.4	1228.6	1227.1	1225.6	1224.1	1222.6	1224.1
172.5°	1234.6	1235.9	1237.2	1238.5	1239.2	1238.4	1236.9	1235.4	1233.9	1232.4	1233.9
175°	1241.5	1242.8	1244.1	1245.4	1246.1	1245.3	1243.8	1242.3	1240.7	1239.2	1240.7
177.5°	1245.4	1246.7	1248.0	1249.3	1250.0	1249.2	1247.7	1246.2	1244.6	1243.1	1244.6
180°	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1315.9	1309.6	1305.5	1302.3	1299.2	1308.6	1296.1	1282.5	1273.1	1266.9	1264.8
5°	1453.6	1440.1	1428.6	1419.2	1421.3	1421.3	1399.4	1375.4	1354.5	1343.0	1330.5
7.5°	1613.3	1598.7	1575.7	1570.5	1566.3	1540.3	1518.3	1474.5	1448.4	1422.3	1399.4
10°	1771.9	1753.1	1731.2	1723.9	1713.5	1681.1	1647.7	1591.4	1559.0	1511.0	1480.8
12.5°	1920.1	1897.1	1875.2	1870.0	1854.4	1826.2	1768.8	1710.4	1655.0	1603.9	1550.7
15°	2044.3	2038.0	2004.6	1983.8	1949.3	1910.7	1898.2	1818.9	1749.0	1695.7	1599.7
17.5°	2148.6	2119.4	2088.1	2074.5	2061.0	2016.1	1971.2	1889.8	1814.7	1736.4	1674.9
20°	2232.1	2199.8	2177.9	2158.0	2151.8	2100.6	2029.7	1957.7	1875.2	1787.6	1707.2
22.5°	2236.3	2232.1	2217.5	2206.0	2193.5	2160.1	2103.8	2014.0	1926.4	1830.4	1725.0
25°	2149.7	2143.4	2185.2	2174.7	2183.1	2170.6	2140.3	2065.2	1962.9	1850.2	1743.7
27.5°	1888.8	1952.5	2018.2	2041.2	2056.8	2101.7	2116.3	2074.5	1992.1	1872.1	1753.1
30°	1534.0	1618.5	1725.0	1782.4	1826.2	1909.7	2018.2	2031.8	1993.2	1897.1	1751.1
32.5°	1204.2	1281.5	1367.0	1434.9	1493.3	1664.4	1810.5	1915.9	1934.7	1884.6	1756.3
35°	970.5	1003.9	1085.3	1150.0	1229.3	1375.4	1547.6	1717.7	1832.4	1838.7	1740.6
37.5°	800.4	818.1	889.1	925.6	972.6	1100.9	1261.6	1483.9	1662.4	1746.9	1696.8
40°	662.6	703.3	744.0	764.9	798.3	887.0	1041.4	1215.7	1436.9	1593.5	1629.0
42.5°	575.0	592.7	618.8	648.0	668.9	746.1	849.4	1009.1	1208.4	1426.5	1524.6
45°	507.2	513.4	540.6	559.3	581.2	635.5	708.6	842.1	1017.4	1232.4	1399.4
47.5°	450.8	463.3	477.9	489.4	504.0	545.8	608.4	705.4	859.9	1051.9	1231.4
50°	400.7	408.0	426.8	432.0	442.5	471.7	519.7	593.8	721.1	874.5	1060.2
52.5°	353.8	367.3	374.6	381.9	391.3	415.3	446.6	507.2	603.2	747.2	904.7
55°	317.2	321.4	331.8	338.1	345.4	362.1	389.2	434.1	509.2	624.0	773.3
57.5°	281.8	281.8	292.2	297.4	304.7	317.2	341.2	375.7	429.9	515.5	652.2
60°	244.2	245.2	253.6	259.8	261.9	274.4	294.3	321.4	363.2	425.8	537.4
62.5°	210.8	216.0	220.2	222.3	229.6	236.9	253.6	272.4	301.6	356.9	436.2
65°	182.6	183.7	186.8	188.9	192.0	200.4	212.9	225.4	250.4	291.1	355.8
67.5°	150.3	154.4	158.6	158.6	161.7	165.9	178.4	188.9	207.7	231.7	275.5
70°	112.7	114.8	121.1	124.2	128.4	135.7	141.9	148.2	162.8	180.5	213.9
72.5°	93.9	93.9	96.0	97.0	97.0	102.3	111.7	117.9	125.2	137.7	160.7
75°	75.1	75.1	78.3	77.2	79.3	81.4	82.4	86.6	90.8	100.2	113.7
77.5°	59.5	60.5	60.5	61.6	61.6	62.6	63.7	65.7	67.8	73.0	79.3
80°	43.8	44.9	44.9	45.9	45.9	47.0	48.0	49.0	51.1	53.2	56.4
82.5°	30.3	31.3	31.3	32.3	31.3	32.3	33.4	33.4	34.4	36.5	37.6
85°	17.7	17.7	18.8	17.7	17.7	17.7	18.8	18.8	19.8	23.0	23.0
87.5°	5.2	6.3	5.2	6.3	6.3	6.3	6.3	7.3	7.3	8.3	9.4
90°	28.5	28.1	27.6	27.4	27.0	26.1	25.2	24.4	23.5	20.7	17.9
92.5°	43.0	43.4	43.9	44.1	43.8	43.1	42.4	41.8	41.1	39.8	38.5
95°	76.4	76.4	76.4	76.4	76.0	75.1	74.2	73.4	72.5	70.8	69.0
97.5°	110.1	110.4	110.6	110.7	110.2	109.1	108.0	106.9	105.8	104.5	103.2
100°	148.0	147.6	147.1	146.9	146.6	145.9	145.3	144.6	144.0	142.9	141.8
102.5°	189.5	189.7	189.9	190.0	189.7	189.0	188.4	187.7	187.1	185.6	184.0
105°	232.3	231.8	231.4	231.2	231.2	231.2	231.2	231.2	231.2	229.2	227.3
107.5°	278.6	278.9	279.1	279.2	278.9	278.2	277.6	276.9	276.3	275.4	274.5
110°	325.1	325.6	326.0	326.2	325.8	324.9	324.0	323.2	322.3	321.9	321.4

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	373.2	373.2	373.2	373.2	372.7	371.6	370.5	369.4	368.3	368.3	368.3
115°	417.7	418.0	418.2	418.3	418.2	418.0	417.7	417.5	417.3	417.7	418.2
117.5°	463.7	464.3	465.0	465.3	465.3	465.3	465.3	465.3	465.3	465.7	466.2
120°	511.2	511.7	512.1	512.3	512.4	512.6	512.9	513.1	513.3	514.4	515.5
122.5°	557.7	558.4	559.1	559.4	559.7	560.4	561.0	561.7	562.3	562.7	563.2
125°	604.2	605.1	606.0	606.4	606.8	607.7	608.6	609.4	610.3	610.7	611.2
127.5°	650.2	651.1	652.0	652.4	653.1	654.4	655.7	657.0	658.3	658.7	659.2
130°	696.6	698.1	699.6	700.4	700.8	701.7	702.6	703.4	704.3	705.0	705.6
132.5°	742.8	743.9	745.0	745.5	746.0	747.1	748.2	749.3	750.4	750.8	751.2
135°	790.4	790.9	791.3	791.5	791.9	792.8	793.7	794.6	795.5	795.7	795.9
137.5°	834.0	834.6	835.3	835.6	836.1	837.2	838.3	839.4	840.5	839.9	839.2
140°	877.9	879.4	880.9	881.7	881.8	882.0	882.2	882.4	882.6	882.4	882.2
142.5°	920.1	921.2	922.3	922.8	922.9	923.1	923.4	923.6	923.8	923.4	922.9
145°	960.8	961.7	962.6	963.0	963.1	963.3	963.5	963.7	963.9	963.3	962.6
147.5°	998.9	1000.2	1001.5	1002.2	1002.2	1002.2	1002.2	1002.2	1002.2	1001.5	1000.9
150°	1034.1	1035.4	1036.7	1037.4	1037.4	1037.4	1037.4	1037.4	1037.4	1037.0	1036.6
152.5°	1068.0	1069.1	1070.2	1070.7	1070.5	1070.1	1069.6	1069.2	1068.8	1068.6	1068.4
155°	1099.3	1100.8	1102.3	1103.1	1102.7	1101.8	1100.9	1100.0	1099.1	1098.9	1098.7
157.5°	1127.2	1128.5	1129.8	1130.5	1130.1	1129.2	1128.3	1127.5	1126.6	1126.4	1126.2
160°	1153.8	1154.7	1155.6	1156.0	1155.5	1154.4	1153.3	1152.2	1151.1	1151.1	1151.1
162.5°	1175.7	1177.2	1178.7	1179.5	1179.0	1177.9	1176.8	1175.7	1174.6	1174.4	1174.2
165°	1195.3	1196.8	1198.3	1199.1	1198.4	1197.1	1195.8	1194.5	1193.2	1193.2	1193.2
167.5°	1212.4	1213.7	1215.0	1215.7	1215.0	1213.7	1212.4	1211.1	1209.8	1209.6	1209.4
170°	1225.6	1227.1	1228.6	1229.4	1228.6	1227.1	1225.6	1224.1	1222.6	1222.6	1222.6
172.5°	1235.4	1236.9	1238.4	1239.2	1238.5	1237.2	1235.9	1234.6	1233.3	1233.3	1233.3
175°	1242.3	1243.8	1245.3	1246.1	1245.4	1244.1	1242.8	1241.5	1240.2	1240.2	1240.2
177.5°	1246.2	1247.7	1249.2	1250.0	1249.3	1248.0	1246.7	1245.4	1244.1	1244.1	1244.1
180°	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1261.6	1256.4	1251.2	1251.2	1239.7	1229.3	1224.1	1226.2	1219.9	1211.5	1203.2
5°	1316.9	1296.1	1291.9	1280.4	1264.8	1242.8	1231.4	1220.9	1208.4	1191.7	1176.1
7.5°	1368.1	1340.9	1326.3	1314.9	1284.6	1254.3	1229.3	1212.6	1190.7	1165.6	1146.8
10°	1434.9	1384.8	1369.1	1343.0	1300.2	1257.5	1228.2	1201.1	1170.8	1141.6	1116.6
12.5°	1488.1	1430.7	1401.5	1375.4	1320.1	1265.8	1216.8	1183.4	1146.8	1114.5	1082.1
15°	1548.6	1483.9	1432.8	1401.5	1331.6	1265.8	1210.5	1163.5	1122.8	1083.2	1055.0
17.5°	1577.8	1496.4	1473.5	1428.6	1327.4	1261.6	1193.8	1143.7	1094.7	1048.8	1015.4
20°	1623.7	1528.8	1471.4	1441.1	1351.4	1254.3	1175.0	1117.6	1066.5	1017.4	982.0
22.5°	1626.9	1523.6	1486.0	1428.6	1318.0	1232.4	1158.3	1088.4	1028.9	983.0	946.5
25°	1619.6	1514.2	1462.0	1416.1	1324.2	1219.9	1124.9	1056.1	997.6	944.4	901.6
27.5°	1616.4	1487.0	1438.0	1392.1	1288.8	1183.4	1105.1	1026.8	960.1	913.1	869.3
30°	1612.3	1457.8	1398.3	1345.1	1250.2	1155.2	1061.3	993.4	929.8	870.3	826.5
32.5°	1585.1	1418.2	1357.6	1301.3	1199.0	1104.1	1030.0	958.0	889.1	833.8	794.1
35°	1576.8	1381.6	1302.3	1241.8	1141.6	1057.1	978.8	919.4	854.7	799.3	752.4
37.5°	1552.8	1344.1	1258.5	1181.3	1076.9	996.6	939.2	879.7	817.1	757.6	720.0
40°	1511.0	1300.2	1203.2	1123.9	1016.4	935.0	881.8	838.0	776.4	723.2	677.3
42.5°	1449.5	1255.4	1151.0	1067.5	948.6	872.4	828.6	786.8	734.6	679.3	641.8
45°	1378.5	1195.9	1098.8	1006.0	884.9	810.8	764.9	739.9	691.9	644.9	601.1
47.5°	1281.5	1134.3	1038.3	942.3	819.2	747.2	710.6	685.6	652.2	601.1	565.6
50°	1159.4	1055.0	964.2	878.7	754.5	685.6	649.1	630.3	602.1	565.6	531.2
52.5°	1023.7	963.2	888.0	808.7	688.7	624.0	590.6	576.0	555.2	520.7	491.5
55°	887.0	860.9	809.8	731.5	619.9	566.6	537.4	518.6	503.0	477.9	452.9
57.5°	764.9	752.4	716.9	656.4	562.5	507.2	482.1	469.6	457.1	438.3	413.2
60°	638.6	652.2	615.7	585.4	499.9	451.9	429.9	416.4	410.1	393.4	377.8
62.5°	529.1	541.6	520.7	497.8	437.2	394.5	380.9	368.4	364.2	349.6	333.9
65°	429.9	445.6	429.9	417.4	380.9	345.4	328.7	322.5	318.3	308.9	296.4
67.5°	342.3	357.9	350.6	335.0	323.5	294.3	284.9	278.6	276.5	269.2	258.8
70°	257.8	279.7	281.8	272.4	261.9	248.4	242.1	240.0	234.8	228.5	222.3
72.5°	185.7	210.8	211.8	211.8	205.6	205.6	199.3	196.2	196.2	189.9	182.6
75°	136.7	153.4	155.5	157.6	160.7	163.8	159.7	159.7	158.6	152.4	149.2
77.5°	90.8	105.4	110.6	117.9	122.1	122.1	124.2	126.3	124.2	121.1	119.0
80°	58.4	68.9	75.1	79.3	85.6	88.7	91.8	92.9	90.8	89.7	86.6
82.5°	38.6	41.7	44.9	50.1	57.4	62.6	62.6	61.6	63.7	62.6	61.6
85°	21.9	24.0	25.0	26.1	30.3	35.5	36.5	37.6	39.7	37.6	35.5
87.5°	8.3	9.4	9.4	9.4	11.5	12.5	15.7	19.8	18.8	16.7	16.7
90°	15.0	12.2	10.8	9.7	7.5	5.4	3.2	1.0	3.2	5.4	7.5
92.5°	37.2	35.9	35.3	34.6	33.3	32.0	30.7	29.4	30.7	32.0	33.3
95°	67.3	65.6	64.7	63.9	62.4	60.9	59.3	57.8	59.3	60.9	62.4
97.5°	101.9	100.6	99.9	99.4	98.3	97.2	96.1	95.0	96.1	97.2	98.3
100°	140.7	139.6	139.1	138.4	137.1	135.8	134.5	133.2	134.5	135.8	137.1
102.5°	182.5	181.0	180.2	179.9	179.2	178.6	177.9	177.3	177.9	178.6	179.2
105°	225.3	223.4	222.4	222.2	221.7	221.3	220.8	220.4	220.8	221.3	221.7
107.5°	273.6	272.7	272.3	272.2	272.0	271.8	271.6	271.4	271.6	271.8	272.0
110°	321.0	320.5	320.3	320.1	319.7	319.2	318.8	318.4	318.8	319.2	319.7

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	368.3	368.3	368.3	368.2	368.0	367.8	367.6	367.4	367.6	367.8	368.0
115°	418.6	419.1	419.3	419.0	418.3	417.6	417.0	416.3	417.0	417.6	418.3
117.5°	466.6	467.1	467.3	467.2	467.0	466.7	466.5	466.3	466.5	466.7	467.0
120°	516.6	517.7	518.2	517.5	516.2	514.9	513.6	512.3	513.6	514.9	516.2
122.5°	563.6	564.1	564.3	563.9	563.0	562.1	561.2	560.3	561.2	562.1	563.0
125°	611.6	612.1	612.3	612.0	611.3	610.6	610.0	609.3	610.0	610.6	611.3
127.5°	659.6	660.1	660.3	659.6	658.3	657.0	655.7	654.4	655.7	657.0	658.3
130°	706.3	707.0	707.3	706.4	704.7	702.9	701.2	699.4	701.2	702.9	704.7
132.5°	751.7	752.1	752.3	751.4	749.7	748.0	746.2	744.5	746.2	748.0	749.7
135°	796.1	796.3	796.4	795.8	794.5	793.2	791.9	790.6	791.9	793.2	794.5
137.5°	838.6	837.9	837.6	837.1	836.0	834.9	833.8	832.7	833.8	834.9	836.0
140°	882.0	881.8	881.7	881.2	880.1	879.0	877.9	876.8	877.9	879.0	880.1
142.5°	922.5	922.0	921.8	921.3	920.2	919.1	918.0	916.9	918.0	919.1	920.2
145°	962.0	961.3	961.0	960.8	960.3	959.9	959.4	959.0	959.4	959.9	960.3
147.5°	1000.2	999.5	999.2	998.8	997.9	997.0	996.2	995.3	996.2	997.0	997.9
150°	1036.1	1035.7	1035.5	1035.3	1034.8	1034.4	1033.9	1033.5	1033.9	1034.4	1034.8
152.5°	1068.1	1067.9	1067.8	1067.5	1066.8	1066.1	1065.5	1064.8	1065.5	1066.1	1066.8
155°	1098.5	1098.3	1098.2	1098.2	1098.2	1098.2	1098.2	1098.2	1098.2	1098.2	1098.2
157.5°	1125.9	1125.7	1125.6	1125.7	1125.9	1126.2	1126.4	1126.6	1126.4	1126.2	1125.9
160°	1151.1	1151.1	1151.1	1151.3	1151.7	1152.2	1152.6	1153.0	1152.6	1152.2	1151.7
162.5°	1173.9	1173.7	1173.6	1173.9	1174.6	1175.2	1175.9	1176.5	1175.9	1175.2	1174.6
165°	1193.2	1193.2	1193.2	1193.5	1194.2	1194.8	1195.5	1196.1	1195.5	1194.8	1194.2
167.5°	1209.2	1209.0	1208.9	1209.3	1210.2	1211.1	1211.9	1212.8	1211.9	1211.1	1210.2
170°	1222.6	1222.6	1222.6	1223.0	1223.9	1224.8	1225.6	1226.5	1225.6	1224.8	1223.9
172.5°	1233.3	1233.3	1233.3	1233.7	1234.6	1235.5	1236.4	1237.3	1236.4	1235.5	1234.6
175°	1240.2	1240.2	1240.2	1240.6	1241.5	1242.4	1243.2	1244.1	1243.2	1242.4	1241.5
177.5°	1244.1	1244.1	1244.1	1244.5	1245.4	1246.3	1247.1	1248.0	1247.1	1246.3	1245.4
180°	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1203.2	1198.0	1195.9	1190.7	1178.2	1169.8	1160.4	1154.1	1155.2	1150.0	1153.1
5°	1165.6	1164.6	1157.3	1146.8	1129.1	1119.7	1103.0	1094.7	1090.5	1091.5	1085.3
7.5°	1134.3	1124.9	1119.7	1103.0	1086.3	1066.5	1052.9	1045.6	1039.4	1033.1	1028.9
10°	1098.8	1090.5	1082.1	1064.4	1041.4	1022.7	1003.9	996.6	987.2	983.0	979.9
12.5°	1061.3	1056.1	1045.6	1024.8	998.7	980.9	959.0	954.8	942.3	934.0	931.9
15°	1026.8	1023.7	1004.9	980.9	954.8	937.1	918.3	905.8	884.9	889.1	881.8
17.5°	990.3	976.7	965.3	932.9	920.4	893.3	871.4	865.1	850.5	841.1	831.7
20°	949.6	941.3	926.7	905.8	875.5	844.2	827.5	817.1	808.7	794.1	790.0
22.5°	911.0	900.6	888.0	860.9	834.8	808.7	785.8	776.4	766.0	755.5	749.3
25°	880.7	865.1	851.5	818.1	792.0	770.1	755.5	739.9	725.3	719.0	716.9
27.5°	833.8	824.4	810.8	779.5	755.5	731.5	718.0	707.5	691.9	684.6	678.3
30°	803.5	784.7	769.1	744.0	720.0	694.0	681.4	668.9	659.5	650.1	642.8
32.5°	762.8	748.2	735.7	710.6	686.6	662.6	649.1	630.3	625.1	617.8	609.4
35°	723.2	713.8	700.2	673.1	647.0	630.3	615.7	597.9	591.7	586.5	579.2
37.5°	685.6	672.0	662.6	636.6	613.6	593.8	582.3	567.7	563.5	557.2	552.0
40°	653.3	639.7	630.3	604.2	580.2	559.3	552.0	537.4	531.2	523.9	520.7
42.5°	616.7	605.3	592.7	573.9	548.9	528.0	513.4	505.1	496.7	493.6	487.3
45°	578.1	567.7	558.3	537.4	511.3	496.7	484.2	472.7	466.5	461.2	457.1
47.5°	544.7	535.3	522.8	499.9	479.0	465.4	452.9	441.4	435.2	428.9	423.7
50°	506.1	500.9	487.3	465.4	445.6	429.9	418.5	408.0	403.8	396.5	388.2
52.5°	471.7	462.3	450.8	433.1	415.3	396.5	380.9	374.6	367.3	363.2	355.8
55°	431.0	424.7	412.2	396.5	377.8	362.1	350.6	342.3	332.9	328.7	319.3
57.5°	396.5	385.1	378.8	359.0	341.2	325.6	317.2	308.9	298.5	292.2	288.0
60°	359.0	348.5	339.1	322.5	309.9	293.2	280.7	273.4	266.1	257.8	253.6
62.5°	322.5	314.1	302.6	289.1	273.4	259.8	250.4	240.0	235.8	227.5	224.4
65°	282.8	276.5	267.1	251.5	239.0	227.5	218.1	209.8	205.6	202.4	200.4
67.5°	247.3	239.0	232.7	219.1	205.6	196.2	191.0	185.7	180.5	177.4	174.3
70°	210.8	204.5	198.3	185.7	176.4	168.0	163.8	159.7	156.5	153.4	150.3
72.5°	173.2	170.1	163.8	155.5	148.2	141.9	138.8	133.6	130.4	125.2	123.1
75°	143.0	137.7	134.6	127.3	121.1	115.8	111.7	105.4	101.2	99.1	98.1
77.5°	112.7	110.6	106.4	100.2	97.0	91.8	85.6	83.5	81.4	81.4	80.4
80°	84.5	81.4	78.3	73.0	69.9	65.7	65.7	65.7	64.7	65.7	64.7
82.5°	57.4	55.3	53.2	50.1	49.0	49.0	50.1	50.1	50.1	50.1	50.1
85°	33.4	33.4	33.4	34.4	33.4	33.4	34.4	35.5	34.4	34.4	33.4
87.5°	15.7	15.7	16.7	16.7	17.7	17.7	17.7	17.7	17.7	17.7	18.8
90°	9.7	10.8	12.2	15.0	17.9	20.7	23.5	24.4	25.2	26.1	27.0
92.5°	34.6	35.3	35.9	37.2	38.5	39.8	41.1	41.8	42.4	43.1	43.8
95°	63.9	64.7	65.6	67.3	69.0	70.8	72.5	73.4	74.2	75.1	76.0
97.5°	99.4	99.9	100.6	101.9	103.2	104.5	105.8	106.9	108.0	109.1	110.2
100°	138.4	139.1	139.6	140.7	141.8	142.9	144.0	144.6	145.3	145.9	146.6
102.5°	179.9	180.2	181.0	182.5	184.0	185.6	187.1	187.7	188.4	189.0	189.7
105°	222.2	222.4	223.4	225.3	227.3	229.2	231.2	231.2	231.2	231.2	231.2
107.5°	272.2	272.3	272.7	273.6	274.5	275.4	276.3	276.9	277.6	278.2	278.9
110°	320.1	320.3	320.5	321.0	321.4	321.9	322.3	323.2	324.0	324.9	325.8

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	368.2	368.3	368.3	368.3	368.3	368.3	368.3	369.4	370.5	371.6	372.7
115°	419.0	419.3	419.1	418.6	418.2	417.7	417.3	417.5	417.7	418.0	418.2
117.5°	467.2	467.3	467.1	466.6	466.2	465.7	465.3	465.3	465.3	465.3	465.3
120°	517.5	518.2	517.7	516.6	515.5	514.4	513.3	513.1	512.9	512.6	512.4
122.5°	563.9	564.3	564.1	563.6	563.2	562.7	562.3	561.7	561.0	560.4	559.7
125°	612.0	612.3	612.1	611.6	611.2	610.7	610.3	609.4	608.6	607.7	606.8
127.5°	659.6	660.3	660.1	659.6	659.2	658.7	658.3	657.0	655.7	654.4	653.1
130°	706.4	707.3	707.0	706.3	705.6	705.0	704.3	703.4	702.6	701.7	700.8
132.5°	751.4	752.3	752.1	751.7	751.2	750.8	750.4	749.3	748.2	747.1	746.0
135°	795.8	796.4	796.3	796.1	795.9	795.7	795.5	794.6	793.7	792.8	791.9
137.5°	837.1	837.6	837.9	838.6	839.2	839.9	840.5	839.4	838.3	837.2	836.1
140°	881.2	881.7	881.8	882.0	882.2	882.4	882.6	882.4	882.2	882.0	881.8
142.5°	921.3	921.8	922.0	922.5	922.9	923.4	923.8	923.6	923.4	923.1	922.9
145°	960.8	961.0	961.3	962.0	962.6	963.3	963.9	963.7	963.5	963.3	963.1
147.5°	998.8	999.2	999.5	1000.2	1000.9	1001.5	1002.2	1002.2	1002.2	1002.2	1002.2
150°	1035.3	1035.5	1035.7	1036.1	1036.6	1037.0	1037.4	1037.4	1037.4	1037.4	1037.4
152.5°	1067.5	1067.8	1067.9	1068.1	1068.4	1068.6	1068.8	1069.2	1069.6	1070.1	1070.5
155°	1098.2	1098.2	1098.3	1098.5	1098.7	1098.9	1099.1	1100.0	1100.9	1101.8	1102.7
157.5°	1125.7	1125.6	1125.7	1125.9	1126.2	1126.4	1126.6	1127.5	1128.3	1129.2	1130.1
160°	1151.3	1151.1	1151.1	1151.1	1151.1	1151.1	1151.1	1152.2	1153.3	1154.4	1155.5
162.5°	1173.9	1173.6	1173.7	1173.9	1174.2	1174.4	1174.6	1175.7	1176.8	1177.9	1179.0
165°	1193.5	1193.2	1193.2	1193.2	1193.2	1193.2	1193.2	1194.5	1195.8	1197.1	1198.4
167.5°	1209.3	1208.9	1209.0	1209.2	1209.4	1209.6	1209.8	1211.1	1212.4	1213.7	1215.0
170°	1223.0	1222.6	1222.6	1222.6	1222.6	1222.6	1222.6	1224.1	1225.6	1227.1	1228.6
172.5°	1233.7	1233.3	1233.3	1233.3	1233.3	1233.3	1233.3	1234.6	1235.9	1237.2	1238.5
175°	1240.6	1240.2	1240.2	1240.2	1240.2	1240.2	1240.2	1241.5	1242.8	1244.1	1245.4
177.5°	1244.5	1244.1	1244.1	1244.1	1244.1	1244.1	1244.1	1245.4	1246.7	1248.0	1249.3
180°	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1152.1	1153.1	1150.0	1143.7	1142.7	1144.8	1151.0	1148.9	1143.7	1153.1	1144.8
5°	1088.4	1083.2	1081.1	1083.2	1076.9	1073.8	1080.1	1076.9	1080.1	1081.1	1084.2
7.5°	1026.8	1027.9	1021.6	1022.7	1014.3	1016.4	1016.4	1016.4	1019.5	1021.6	1025.8
10°	973.6	975.7	968.4	969.4	963.2	959.0	962.1	968.4	968.4	968.4	970.5
12.5°	930.8	921.4	916.2	915.2	907.9	905.8	912.0	914.1	919.4	919.4	922.5
15°	877.6	875.5	871.4	871.4	853.6	857.8	859.9	867.2	877.6	869.3	871.4
17.5°	829.6	824.4	819.2	817.1	815.0	808.7	817.1	816.0	822.3	823.3	826.5
20°	786.8	782.7	772.2	773.3	775.3	766.0	771.2	771.2	777.4	783.7	791.0
22.5°	745.1	740.9	735.7	737.8	731.5	729.4	729.4	734.6	742.0	747.2	746.1
25°	712.7	705.4	702.3	699.2	696.0	698.1	695.0	700.2	705.4	708.6	705.4
27.5°	676.2	673.1	666.8	663.7	658.5	660.6	662.6	666.8	669.9	669.9	673.1
30°	640.7	636.6	634.5	631.3	631.3	627.2	628.2	632.4	635.5	638.6	642.8
32.5°	606.3	603.2	600.0	600.0	597.9	596.9	595.9	602.1	602.1	608.4	608.4
35°	578.1	572.9	572.9	567.7	569.8	568.7	566.6	570.8	571.9	576.0	575.0
37.5°	546.8	546.8	544.7	539.5	535.3	536.4	541.6	541.6	544.7	543.7	546.8
40°	515.5	513.4	513.4	510.3	509.2	508.2	509.2	510.3	515.5	514.5	515.5
42.5°	484.2	485.2	480.0	480.0	480.0	476.9	477.9	479.0	481.1	483.2	486.3
45°	453.9	451.9	450.8	448.7	446.6	447.7	446.6	450.8	449.8	451.9	455.0
47.5°	421.6	418.5	417.4	413.2	413.2	415.3	414.3	417.4	418.5	421.6	419.5
50°	390.3	386.1	383.0	384.0	377.8	379.8	379.8	383.0	386.1	387.2	389.2
52.5°	353.8	352.7	351.7	346.5	345.4	344.4	345.4	346.5	350.6	353.8	354.8
55°	318.3	317.2	311.0	308.9	305.8	305.8	307.8	308.9	316.2	317.2	321.4
57.5°	285.9	282.8	275.5	274.4	274.4	274.4	271.3	275.5	277.6	282.8	282.8
60°	250.4	250.4	244.2	244.2	245.2	244.2	244.2	245.2	245.2	249.4	251.5
62.5°	222.3	221.2	221.2	219.1	218.1	219.1	218.1	218.1	219.1	222.3	225.4
65°	197.2	196.2	195.1	194.1	192.0	192.0	193.1	195.1	195.1	197.2	198.3
67.5°	173.2	173.2	171.1	171.1	170.1	169.1	170.1	169.1	173.2	173.2	174.3
70°	149.2	148.2	145.1	144.0	140.9	141.9	141.9	145.1	146.1	148.2	150.3
72.5°	120.0	120.0	117.9	115.8	116.9	114.8	114.8	115.8	115.8	119.0	120.0
75°	99.1	97.0	96.0	97.0	96.0	98.1	96.0	96.0	98.1	98.1	98.1
77.5°	81.4	81.4	80.4	80.4	81.4	80.4	81.4	81.4	81.4	80.4	81.4
80°	66.8	65.7	65.7	65.7	64.7	64.7	64.7	64.7	64.7	64.7	64.7
82.5°	50.1	50.1	49.0	50.1	50.1	49.0	50.1	49.0	49.0	50.1	50.1
85°	33.4	35.5	33.4	33.4	34.4	34.4	35.5	34.4	35.5	33.4	34.4
87.5°	17.7	18.8	18.8	17.7	17.7	18.8	18.8	18.8	19.8	17.7	18.8
90°	27.4	27.6	28.1	28.5	29.0	29.4	29.0	28.5	28.1	27.6	27.4
92.5°	44.1	43.9	43.4	43.0	42.5	42.1	42.5	43.0	43.4	43.9	44.1
95°	76.4	76.4	76.4	76.4	76.4	76.4	76.4	76.4	76.4	76.4	76.4
97.5°	110.7	110.6	110.4	110.1	109.9	109.7	109.9	110.1	110.4	110.6	110.7
100°	146.9	147.1	147.6	148.0	148.5	148.9	148.5	148.0	147.6	147.1	146.9
102.5°	190.0	189.9	189.7	189.5	189.3	189.1	189.3	189.5	189.7	189.9	190.0
105°	231.2	231.4	231.8	232.3	232.7	233.1	232.7	232.3	231.8	231.4	231.2
107.5°	279.2	279.1	278.9	278.6	278.4	278.2	278.4	278.6	278.9	279.1	279.2
110°	326.2	326.0	325.6	325.1	324.7	324.3	324.7	325.1	325.6	326.0	326.2

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	373.2	373.2	373.2	373.2	373.2	373.2	373.2	373.2	373.2	373.2	373.2
115°	418.3	418.2	418.0	417.7	417.5	417.3	417.5	417.7	418.0	418.2	418.3
117.5°	465.3	465.0	464.3	463.7	463.0	462.4	463.0	463.7	464.3	465.0	465.3
120°	512.3	512.1	511.7	511.2	510.8	510.4	510.8	511.2	511.7	512.1	512.3
122.5°	559.4	559.1	558.4	557.7	557.1	556.4	557.1	557.7	558.4	559.1	559.4
125°	606.4	606.0	605.1	604.2	603.4	602.5	603.4	604.2	605.1	606.0	606.4
127.5°	652.4	652.0	651.1	650.2	649.4	648.5	649.4	650.2	651.1	652.0	652.4
130°	700.4	699.6	698.1	696.6	695.1	693.6	695.1	696.6	698.1	699.6	700.4
132.5°	745.5	745.0	743.9	742.8	741.7	740.6	741.7	742.8	743.9	745.0	745.5
135°	791.5	791.3	790.9	790.4	790.0	789.6	790.0	790.4	790.9	791.3	791.5
137.5°	835.6	835.3	834.6	834.0	833.3	832.7	833.3	834.0	834.6	835.3	835.6
140°	881.7	880.9	879.4	877.9	876.3	874.8	876.3	877.9	879.4	880.9	881.7
142.5°	922.8	922.3	921.2	920.1	919.0	917.9	919.0	920.1	921.2	922.3	922.8
145°	963.0	962.6	961.7	960.8	959.9	959.0	959.9	960.8	961.7	962.6	963.0
147.5°	1002.2	1001.5	1000.2	998.9	997.6	996.3	997.6	998.9	1000.2	1001.5	1002.2
150°	1037.4	1036.7	1035.4	1034.1	1032.8	1031.5	1032.8	1034.1	1035.4	1036.7	1037.4
152.5°	1070.7	1070.2	1069.1	1068.0	1066.9	1065.8	1066.9	1068.0	1069.1	1070.2	1070.7
155°	1103.1	1102.3	1100.8	1099.3	1097.7	1096.2	1097.7	1099.3	1100.8	1102.3	1103.1
157.5°	1130.5	1129.8	1128.5	1127.2	1125.9	1124.6	1125.9	1127.2	1128.5	1129.8	1130.5
160°	1156.0	1155.6	1154.7	1153.8	1152.9	1152.0	1152.9	1153.8	1154.7	1155.6	1156.0
162.5°	1179.5	1178.7	1177.2	1175.7	1174.1	1172.6	1174.1	1175.7	1177.2	1178.7	1179.5
165°	1199.1	1198.3	1196.8	1195.3	1193.7	1192.2	1193.7	1195.3	1196.8	1198.3	1199.1
167.5°	1215.7	1215.0	1213.7	1212.4	1211.1	1209.8	1211.1	1212.4	1213.7	1215.0	1215.7
170°	1229.4	1228.6	1227.1	1225.6	1224.1	1222.6	1224.1	1225.6	1227.1	1228.6	1229.4
172.5°	1239.2	1238.4	1236.9	1235.4	1233.9	1232.4	1233.9	1235.4	1236.9	1238.4	1239.2
175°	1246.1	1245.3	1243.8	1242.3	1240.7	1239.2	1240.7	1242.3	1243.8	1245.3	1246.1
177.5°	1250.0	1249.2	1247.7	1246.2	1244.6	1243.1	1244.6	1246.2	1247.7	1249.2	1250.0
180°	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1153.1	1157.3	1153.1	1144.8	1153.1	1158.3	1163.5	1171.9	1176.1	1176.1	1182.3
5°	1087.4	1095.7	1092.6	1090.5	1098.8	1104.1	1112.4	1122.8	1134.3	1141.6	1150.0
7.5°	1028.9	1034.1	1039.4	1039.4	1047.7	1059.2	1071.7	1084.2	1098.8	1109.3	1115.5
10°	977.8	982.0	985.1	989.3	1001.8	1014.3	1031.0	1046.7	1059.2	1070.7	1081.1
12.5°	928.7	935.0	942.3	945.4	954.8	970.5	986.1	1004.9	1024.8	1036.2	1046.7
15°	881.8	884.9	893.3	902.7	911.0	927.7	947.5	967.4	984.1	1001.8	1011.2
17.5°	833.8	834.8	856.7	851.5	878.7	894.3	904.7	923.5	950.7	965.3	979.9
20°	786.8	797.3	806.7	811.9	826.5	844.2	874.5	889.1	911.0	924.6	937.1
22.5°	750.3	766.0	766.0	778.5	785.8	802.5	824.4	852.6	876.6	886.0	903.7
25°	718.0	725.3	737.8	742.0	755.5	770.1	784.7	815.0	841.1	853.6	866.1
27.5°	676.2	685.6	702.3	702.3	720.0	735.7	753.4	773.3	799.3	817.1	830.7
30°	643.9	653.3	660.6	672.0	679.3	694.0	725.3	739.9	762.8	778.5	795.2
32.5°	613.6	620.9	627.2	639.7	648.0	664.7	681.4	707.5	727.3	742.0	759.7
35°	580.2	587.5	595.9	605.3	617.8	633.4	649.1	671.0	690.8	704.4	719.0
37.5°	548.9	554.1	566.6	572.9	583.3	597.9	617.8	640.7	658.5	668.9	683.5
40°	518.6	522.8	532.2	543.7	551.0	562.5	583.3	603.2	625.1	637.6	649.1
42.5°	486.3	491.5	499.9	511.3	522.8	535.3	546.8	569.8	589.6	600.0	612.6
45°	458.1	461.2	467.5	479.0	490.5	499.9	517.6	538.5	557.2	565.6	579.2
47.5°	424.7	427.8	437.2	442.5	455.0	467.5	485.2	506.1	522.8	531.2	543.7
50°	390.3	393.4	399.7	411.2	419.5	433.1	448.7	466.5	487.3	498.8	506.1
52.5°	356.9	363.2	368.4	377.8	388.2	401.8	416.4	433.1	450.8	462.3	470.6
55°	323.5	328.7	335.0	340.2	352.7	365.2	381.9	397.6	413.2	423.7	433.1
57.5°	285.9	293.2	299.5	309.9	319.3	329.8	348.5	361.1	379.8	387.2	395.5
60°	253.6	260.9	266.1	274.4	282.8	296.4	308.9	324.5	340.2	349.6	360.0
62.5°	226.4	229.6	232.7	241.1	249.4	261.9	274.4	290.1	306.8	312.0	320.4
65°	199.3	202.4	207.7	215.0	221.2	228.5	242.1	254.6	270.3	278.6	281.8
67.5°	176.4	179.5	180.5	185.7	191.0	199.3	206.6	219.1	233.8	239.0	245.2
70°	150.3	155.5	156.5	160.7	162.8	168.0	176.4	185.7	197.2	206.6	211.8
72.5°	120.0	127.3	129.4	135.7	138.8	144.0	150.3	157.6	164.9	169.1	173.2
75°	98.1	100.2	101.2	106.4	111.7	119.0	122.1	126.3	132.5	137.7	141.9
77.5°	81.4	82.4	83.5	83.5	84.5	88.7	95.0	100.2	104.4	106.4	109.6
80°	65.7	64.7	64.7	65.7	65.7	65.7	67.8	75.1	77.2	82.4	81.4
82.5°	51.1	49.0	50.1	49.0	49.0	49.0	49.0	50.1	50.1	53.2	55.3
85°	33.4	34.4	33.4	33.4	32.3	33.4	32.3	32.3	31.3	31.3	30.3
87.5°	17.7	18.8	17.7	17.7	16.7	17.7	16.7	16.7	15.7	15.7	13.6
90°	27.0	26.1	25.2	24.4	23.5	20.7	17.9	15.0	12.2	10.8	9.7
92.5°	43.8	43.1	42.4	41.8	41.1	39.8	38.5	37.2	35.9	35.3	34.6
95°	76.0	75.1	74.2	73.4	72.5	70.8	69.0	67.3	65.6	64.7	63.9
97.5°	110.2	109.1	108.0	106.9	105.8	104.5	103.2	101.9	100.6	99.9	99.4
100°	146.6	145.9	145.3	144.6	144.0	142.9	141.8	140.7	139.6	139.1	138.4
102.5°	189.7	189.0	188.4	187.7	187.1	185.6	184.0	182.5	181.0	180.2	179.9
105°	231.2	231.2	231.2	231.2	231.2	229.2	227.3	225.3	223.4	222.4	222.2
107.5°	278.9	278.2	277.6	276.9	276.3	275.4	274.5	273.6	272.7	272.3	272.2
110°	325.8	324.9	324.0	323.2	322.3	321.9	321.4	321.0	320.5	320.3	320.1

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	372.7	371.6	370.5	369.4	368.3	368.3	368.3	368.3	368.3	368.3	368.2
115°	418.2	418.0	417.7	417.5	417.3	417.7	418.2	418.6	419.1	419.3	419.0
117.5°	465.3	465.3	465.3	465.3	465.3	465.7	466.2	466.6	467.1	467.3	467.2
120°	512.4	512.6	512.9	513.1	513.3	514.4	515.5	516.6	517.7	518.2	517.5
122.5°	559.7	560.4	561.0	561.7	562.3	562.7	563.2	563.6	564.1	564.3	563.9
125°	606.8	607.7	608.6	609.4	610.3	610.7	611.2	611.6	612.1	612.3	612.0
127.5°	653.1	654.4	655.7	657.0	658.3	658.7	659.2	659.6	660.1	660.3	659.6
130°	700.8	701.7	702.6	703.4	704.3	705.0	705.6	706.3	707.0	707.3	706.4
132.5°	746.0	747.1	748.2	749.3	750.4	750.8	751.2	751.7	752.1	752.3	751.4
135°	791.9	792.8	793.7	794.6	795.5	795.7	795.9	796.1	796.3	796.4	795.8
137.5°	836.1	837.2	838.3	839.4	840.5	839.9	839.2	838.6	837.9	837.6	837.1
140°	881.8	882.0	882.2	882.4	882.6	882.4	882.2	882.0	881.8	881.7	881.2
142.5°	922.9	923.1	923.4	923.6	923.8	923.4	922.9	922.5	922.0	921.8	921.3
145°	963.1	963.3	963.5	963.7	963.9	963.3	962.6	962.0	961.3	961.0	960.8
147.5°	1002.2	1002.2	1002.2	1002.2	1002.2	1001.5	1000.9	1000.2	999.5	999.2	998.8
150°	1037.4	1037.4	1037.4	1037.4	1037.4	1037.0	1036.6	1036.1	1035.7	1035.5	1035.3
152.5°	1070.5	1070.1	1069.6	1069.2	1068.8	1068.6	1068.4	1068.1	1067.9	1067.8	1067.5
155°	1102.7	1101.8	1100.9	1100.0	1099.1	1098.9	1098.7	1098.5	1098.3	1098.2	1098.2
157.5°	1130.1	1129.2	1128.3	1127.5	1126.6	1126.4	1126.2	1125.9	1125.7	1125.6	1125.7
160°	1155.5	1154.4	1153.3	1152.2	1151.1	1151.1	1151.1	1151.1	1151.1	1151.1	1151.3
162.5°	1179.0	1177.9	1176.8	1175.7	1174.6	1174.4	1174.2	1173.9	1173.7	1173.6	1173.9
165°	1198.4	1197.1	1195.8	1194.5	1193.2	1193.2	1193.2	1193.2	1193.2	1193.2	1193.5
167.5°	1215.0	1213.7	1212.4	1211.1	1209.8	1209.6	1209.4	1209.2	1209.0	1208.9	1209.3
170°	1228.6	1227.1	1225.6	1224.1	1222.6	1222.6	1222.6	1222.6	1222.6	1222.6	1223.0
172.5°	1238.5	1237.2	1235.9	1234.6	1233.3	1233.3	1233.3	1233.3	1233.3	1233.3	1233.7
175°	1245.4	1244.1	1242.8	1241.5	1240.2	1240.2	1240.2	1240.2	1240.2	1240.2	1240.6
177.5°	1249.3	1248.0	1246.7	1245.4	1244.1	1244.1	1244.1	1244.1	1244.1	1244.1	1244.5
180°	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1	1247.1

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1218.8	1218.8	1218.8	1218.8
2.5°	1187.5	1194.8	1209.5	1222.0
5°	1162.5	1174.0	1195.9	1217.8
7.5°	1132.2	1150.0	1178.2	1208.4
10°	1103.0	1126.0	1160.4	1195.9
12.5°	1073.8	1097.8	1134.3	1180.2
15°	1039.4	1064.4	1108.2	1163.5
17.5°	1009.1	1042.5	1082.1	1137.5
20°	976.7	1001.8	1052.9	1111.4
22.5°	936.1	977.8	1025.8	1087.4
25°	903.7	940.2	988.2	1058.1
27.5°	864.0	906.8	965.3	1026.8
30°	831.7	867.2	921.4	995.5
32.5°	794.1	835.9	892.2	965.3
35°	760.7	796.2	849.4	923.5
37.5°	721.1	759.7	819.2	884.9
40°	686.6	724.2	780.6	842.1
42.5°	644.9	684.6	740.9	793.1
45°	611.5	648.0	692.9	740.9
47.5°	570.8	609.4	653.3	686.6
50°	534.3	569.8	604.2	632.4
52.5°	494.6	527.0	558.3	579.2
55°	458.1	483.2	508.2	522.8
57.5°	415.3	439.3	460.2	468.5
60°	377.8	397.6	411.2	420.5
62.5°	338.1	352.7	363.2	368.4
65°	299.5	309.9	315.1	320.4
67.5°	259.8	269.2	272.4	278.6
70°	218.1	228.5	230.6	233.8
72.5°	186.8	186.8	191.0	195.1
75°	149.2	151.3	153.4	153.4
77.5°	116.9	116.9	119.0	120.0
80°	85.6	86.6	86.6	85.6
82.5°	58.4	60.5	58.4	57.4
85°	32.3	36.5	34.4	34.4
87.5°	13.6	13.6	15.7	13.6
90°	7.5	5.4	3.2	1.0
92.5°	33.3	32.0	30.7	29.4
95°	62.4	60.9	59.3	57.8
97.5°	98.3	97.2	96.1	95.0
100°	137.1	135.8	134.5	133.2
102.5°	179.2	178.6	177.9	177.3
105°	221.7	221.3	220.8	220.4
107.5°	272.0	271.8	271.6	271.4
110°	319.7	319.2	318.8	318.4

TEST NUMBER: P1012699

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	368.0	367.8	367.6	367.4
115°	418.3	417.6	417.0	416.3
117.5°	467.0	466.7	466.5	466.3
120°	516.2	514.9	513.6	512.3
122.5°	563.0	562.1	561.2	560.3
125°	611.3	610.6	610.0	609.3
127.5°	658.3	657.0	655.7	654.4
130°	704.7	702.9	701.2	699.4
132.5°	749.7	748.0	746.2	744.5
135°	794.5	793.2	791.9	790.6
137.5°	836.0	834.9	833.8	832.7
140°	880.1	879.0	877.9	876.8
142.5°	920.2	919.1	918.0	916.9
145°	960.3	959.9	959.4	959.0
147.5°	997.9	997.0	996.2	995.3
150°	1034.8	1034.4	1033.9	1033.5
152.5°	1066.8	1066.1	1065.5	1064.8
155°	1098.2	1098.2	1098.2	1098.2
157.5°	1125.9	1126.2	1126.4	1126.6
160°	1151.7	1152.2	1152.6	1153.0
162.5°	1174.6	1175.2	1175.9	1176.5
165°	1194.2	1194.8	1195.5	1196.1
167.5°	1210.2	1211.1	1211.9	1212.8
170°	1223.9	1224.8	1225.6	1226.5
172.5°	1234.6	1235.5	1236.4	1237.3
175°	1241.5	1242.4	1243.2	1244.1
177.5°	1245.4	1246.3	1247.1	1248.0
180°	1247.1	1247.1	1247.1	1247.1

(END OF REPORT)