

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012700

Luminaire Tested: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012700
REPORT IS A COMBINATION OF REPORTS P993521 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6678.0 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45	45	45
1	97	93	90	86	89	86	83	80	72	69	67	59	57	56	47	46	45	39	39	39
2	89	82	76	71	81	76	71	66	63	60	57	52	50	47	42	40	39	34	34	34
3	82	73	66	60	75	67	61	56	56	52	48	47	43	41	38	35	33	29	29	29
4	75	65	57	51	68	60	53	48	50	45	42	42	38	35	34	31	29	26	26	26
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26	23	23	23
6	64	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20	20	20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18	18	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16	16	16
9	51	39	32	27	47	36	30	25	31	26	23	26	22	20	22	19	17	15	15	15
10	48	36	29	24	44	33	27	23	29	24	20	24	21	18	20	17	15	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13119	13119	13119	13119
5°	13130	15110	13163	11210
10°	13014	18240	13070	9791
15°	12879	20701	12879	8634
20°	12616	22330	12686	7659
25°	12422	21214	12398	6988
30°	12197	14699	12171	6333
35°	11926	9438	11873	5838
40°	11589	6664	11533	5346
45°	11003	5333	10988	4868
50°	10284	4461	10249	4307
55°	9473	3676	9397	3652
60°	8677	3039	8592	3106
65°	7745	2432	7796	2632
70°	6885	1690	7068	2128
75°	5835	1253	6075	1637
80°	4647	831	5044	1227
85°	3304	392	3612	762

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 17515 cd/sqm

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.7	1.8
10°-20°	374.7	5.6
20°-30°	590.1	8.8
30°-40°	613.6	9.2
40°-50°	525.0	7.9
50°-60°	400.3	6.0
60°-70°	256.4	3.8
70°-80°	122.9	1.8
80°-90°	35.0	0.5
90°-100°	262.6	3.9
100°-110°	768.8	11.5
110°-120°	750.8	11.2
120°-130°	597.9	9.0
130°-140°	471.8	7.1
140°-150°	351.9	5.3
150°-160°	245.4	3.7
160°-170°	144.1	2.2
170°-180°	46.9	0.7
0°-30°	1084.5	16.2
0°-40°	1698.2	25.4
0°-60°	2623.4	39.3
0°-90°	3037.7	45.5
90°-120°	1782.3	26.7
90°-150°	3203.9	48.0
90°-180°	3640.0	54.5
0°-180°	6678.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1219	1219	1219	1219	1219	
5°	1218	1447	1221	1074	1218	116
15°	1164	2057	1164	858	1164	327
25°	1058	2119	1056	698	1058	487
35°	924	919	919	569	924	578
45°	741	490	740	448	741	570
55°	523	308	519	306	523	468
65°	320	177	322	192	320	320
75°	153	75	160	98	153	166
85°	34	18	38	34	34	38
90°	2	28	2	28	2	4
95°	33	114	33	114	33	35
105°	114	1246	114	1246	114	121
115°	201	1516	201	1516	201	199
125°	279	1195	279	1195	279	248
135°	327	969	327	969	327	253
145°	373	757	373	757	373	234
155°	424	628	424	628	424	195
165°	463	548	463	548	463	131
175°	483	493	483	493	483	46
180°	484	484	484	484	484	

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1222.0	1230.3	1236.6	1240.8	1251.2	1257.5	1262.7	1272.1	1272.1	1274.2	1278.3
5°	1217.8	1235.5	1248.1	1264.8	1286.7	1297.1	1311.7	1324.2	1342.0	1351.4	1360.8
7.5°	1208.4	1233.5	1259.5	1284.6	1316.9	1337.8	1352.4	1384.8	1407.7	1435.9	1457.8
10°	1195.9	1230.3	1263.7	1302.3	1346.2	1377.5	1399.4	1442.2	1486.0	1525.6	1559.0
12.5°	1180.2	1222.0	1270.0	1316.9	1378.5	1409.8	1445.3	1498.5	1561.1	1611.2	1656.1
15°	1163.5	1211.5	1265.8	1323.2	1400.4	1444.3	1495.4	1560.1	1630.0	1702.0	1763.6
17.5°	1137.5	1198.0	1258.5	1342.0	1432.8	1458.9	1502.7	1591.4	1678.0	1742.7	1817.8
20°	1111.4	1179.2	1255.4	1330.5	1428.6	1489.1	1529.8	1623.7	1716.6	1794.9	1866.9
22.5°	1087.4	1158.3	1237.6	1332.6	1424.4	1484.9	1536.1	1634.2	1741.7	1829.3	1918.0
25°	1058.1	1135.4	1223.0	1312.8	1424.4	1470.3	1526.7	1640.4	1754.2	1855.4	1965.0
27.5°	1026.8	1105.1	1191.7	1283.5	1385.8	1453.6	1509.0	1631.0	1769.8	1878.4	1991.1
30°	995.5	1075.9	1159.4	1241.8	1356.6	1421.3	1484.9	1619.6	1778.2	1902.4	1989.0
32.5°	965.3	1033.1	1115.5	1195.9	1309.6	1380.6	1452.6	1608.1	1781.3	1885.7	1927.4
35°	923.5	994.5	1061.3	1146.8	1261.6	1331.6	1416.1	1607.0	1767.7	1832.4	1811.6
37.5°	884.9	944.4	1008.1	1084.2	1202.2	1292.9	1380.6	1579.9	1722.9	1727.0	1609.1
40°	842.1	891.2	944.4	1024.8	1152.1	1241.8	1336.8	1538.2	1641.5	1579.9	1372.2
42.5°	793.1	836.9	878.7	956.9	1095.7	1195.9	1298.2	1486.0	1523.6	1381.6	1165.6
45°	740.9	776.4	815.0	897.4	1036.2	1135.4	1237.6	1405.6	1367.0	1166.7	961.1
47.5°	686.6	716.9	754.5	829.6	972.6	1073.8	1170.8	1290.9	1192.8	977.8	805.6
50°	632.4	656.4	692.9	770.1	907.9	999.7	1089.5	1167.7	1030.0	839.0	665.8
52.5°	579.2	597.9	635.5	701.3	834.8	922.5	987.2	1017.4	877.6	692.9	578.1
55°	522.8	543.7	568.7	635.5	768.0	832.7	875.5	874.5	730.5	587.5	477.9
57.5°	468.5	487.3	509.2	576.0	683.5	727.3	763.9	746.1	609.4	481.1	410.1
60°	420.5	431.0	455.0	511.3	592.7	630.3	651.2	620.9	497.8	405.9	339.1
62.5°	368.4	378.8	398.6	451.9	501.9	521.8	539.5	500.9	411.2	330.8	290.1
65°	320.4	333.9	346.5	389.2	416.4	440.4	438.3	405.9	321.4	269.2	235.8
67.5°	278.6	283.8	294.3	320.4	332.9	350.6	351.7	315.1	258.8	219.1	199.3
70°	233.8	239.0	246.3	258.8	267.1	271.3	269.2	236.9	195.1	171.1	153.4
72.5°	195.1	194.1	199.3	199.3	207.7	206.6	200.4	175.3	148.2	128.4	117.9
75°	153.4	154.4	155.5	153.4	150.3	146.1	140.9	122.1	104.4	95.0	85.6
77.5°	120.0	117.9	119.0	111.7	107.5	103.3	96.0	86.6	72.0	69.9	65.7
80°	85.6	84.5	83.5	80.4	71.0	66.8	61.6	56.4	53.2	51.1	50.1
82.5°	57.4	57.4	55.3	49.0	43.8	40.7	39.7	37.6	34.4	34.4	33.4
85°	34.4	33.4	31.3	25.0	21.9	21.9	21.9	21.9	19.8	19.8	18.8
87.5°	13.6	12.5	9.4	9.4	8.3	8.3	8.3	7.3	7.3	6.3	6.3
90°	2.0	3.9	5.9	8.8	10.8	11.8	12.7	15.7	18.6	21.6	24.5
92.5°	14.7	21.6	31.3	40.2	50.0	58.8	67.6	98.9	150.9	201.8	182.2
95°	33.3	36.2	47.0	63.7	89.1	108.2	127.4	210.6	356.6	517.3	580.9
97.5°	52.9	53.9	62.7	77.4	102.9	124.0	145.0	227.3	396.8	667.1	893.4
100°	72.5	73.5	80.3	94.0	117.6	136.7	155.8	224.3	369.3	627.0	927.7
102.5°	93.1	95.0	100.9	113.6	134.2	151.4	168.5	228.3	345.8	568.2	864.1
105°	113.6	116.6	122.5	134.2	152.8	168.0	183.2	236.1	337.0	522.2	787.6
107.5°	135.2	138.1	144.0	155.8	173.4	187.6	201.8	248.8	335.0	488.8	720.0
110°	158.7	161.6	166.5	177.3	194.0	207.7	221.4	265.5	339.9	471.2	664.2

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	180.3	183.2	188.1	198.9	215.5	228.8	242.0	282.1	349.7	461.4	627.0
115°	200.8	204.7	210.6	220.4	237.1	250.3	263.5	300.8	360.5	460.4	602.5
117.5°	221.4	226.3	231.2	240.0	258.6	270.8	283.1	320.3	374.2	461.4	585.8
120°	243.0	245.9	250.8	260.6	279.2	291.4	303.7	339.0	389.9	465.3	575.1
122.5°	261.6	264.5	269.4	280.2	297.8	311.0	324.3	358.6	404.6	472.2	568.2
125°	279.2	281.2	287.0	297.8	316.4	329.6	342.9	377.2	420.3	479.1	562.3
127.5°	292.9	295.9	302.7	313.5	334.1	347.3	360.5	393.8	433.0	486.9	559.4
130°	305.7	308.6	317.4	329.2	349.7	363.0	376.2	408.5	445.7	494.7	556.4
132.5°	315.4	319.4	329.2	343.9	364.4	377.2	389.9	421.3	457.5	500.6	555.5
135°	327.2	331.1	341.9	356.6	377.2	390.4	403.6	434.0	467.3	506.5	554.5
137.5°	338.0	341.9	352.7	368.4	388.9	401.2	413.4	442.8	475.1	510.4	552.5
140°	348.8	353.7	363.5	379.1	398.7	411.0	423.2	451.6	481.0	514.3	551.5
142.5°	360.5	364.4	375.2	388.9	408.5	419.8	431.0	458.5	486.9	517.3	549.6
145°	373.2	376.2	385.0	399.7	416.4	427.6	438.9	464.4	490.8	518.2	547.6
147.5°	386.0	387.9	396.8	409.5	426.2	436.0	445.7	469.3	493.7	518.2	544.7
150°	398.7	399.7	407.5	420.3	434.0	442.8	451.6	474.2	494.7	518.2	540.8
152.5°	411.5	411.5	419.3	430.1	441.8	450.2	458.5	477.1	496.7	515.3	535.9
155°	424.2	424.2	430.1	439.9	450.6	457.5	464.4	481.0	496.7	513.3	530.0
157.5°	434.0	435.0	439.9	448.7	458.5	463.9	469.3	483.0	497.7	510.4	525.1
160°	445.7	445.7	449.7	457.5	464.4	469.3	474.2	485.9	497.7	508.4	519.2
162.5°	454.6	454.6	457.5	463.4	469.3	473.2	477.1	486.9	496.7	504.5	513.3
165°	463.4	462.4	464.4	469.3	473.2	476.6	480.0	487.9	494.7	500.6	507.5
167.5°	470.2	469.3	470.2	474.2	477.1	479.6	482.0	487.9	493.7	496.7	501.6
170°	476.1	474.2	475.1	478.1	480.0	481.0	482.0	486.9	490.8	492.8	495.7
172.5°	480.0	479.1	479.1	481.0	482.0	482.5	483.0	486.9	489.8	489.8	490.8
175°	483.0	482.0	481.0	483.0	483.0	483.4	483.9	485.9	487.9	486.9	486.9
177.5°	484.9	483.9	483.0	483.9	483.9	483.9	483.9	484.9	486.9	484.9	483.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1286.7	1286.7	1296.1	1305.5	1300.2	1303.4	1314.9	1310.7	1319.0	1318.0	1321.1
5°	1383.7	1395.2	1404.6	1424.4	1427.6	1424.4	1444.3	1449.5	1458.9	1447.4	1452.6
7.5°	1493.3	1517.3	1540.3	1569.5	1578.9	1581.0	1591.4	1606.0	1618.5	1595.6	1607.0
10°	1599.7	1636.3	1683.2	1709.3	1732.3	1740.6	1749.0	1758.4	1773.0	1786.5	1776.1
12.5°	1714.5	1767.7	1812.6	1859.6	1887.8	1884.6	1908.6	1914.9	1926.4	1929.5	1933.7
15°	1808.4	1883.6	1911.8	1981.7	1987.9	2008.8	2035.9	2059.9	2063.1	2056.8	2056.8
17.5°	1898.2	1962.9	2013.0	2069.3	2080.8	2098.5	2133.0	2144.5	2148.6	2147.6	2147.6
20°	1971.2	2014.0	2098.5	2145.5	2164.3	2187.2	2211.2	2225.9	2229.0	2233.2	2226.9
22.5°	2019.2	2083.9	2152.8	2191.4	2207.1	2215.4	2231.1	2235.3	2230.0	2231.1	2232.1
25°	2056.8	2120.5	2162.2	2172.6	2171.6	2161.2	2149.7	2129.9	2127.8	2119.4	2102.7
27.5°	2067.2	2091.2	2086.0	2043.2	2000.5	1996.3	1927.4	1889.8	1847.1	1853.3	1829.3
30°	2010.9	1979.6	1905.5	1797.0	1752.1	1679.0	1601.8	1521.5	1490.2	1455.7	1519.4
32.5°	1873.1	1761.5	1630.0	1489.1	1414.0	1349.3	1266.9	1208.4	1175.0	1146.8	1201.1
35°	1665.5	1491.2	1316.9	1183.4	1121.8	1063.4	986.1	956.9	915.2	919.4	924.6
37.5°	1398.3	1206.3	1074.8	943.4	902.7	878.7	822.3	777.4	762.8	758.6	758.6
40°	1147.9	990.3	873.4	770.1	738.8	719.0	674.1	653.3	637.6	633.4	638.6
42.5°	949.6	815.0	724.2	655.3	633.4	608.4	589.6	563.5	560.4	553.1	562.5
45°	797.3	680.4	612.6	562.5	543.7	534.3	513.4	497.8	491.5	490.5	497.8
47.5°	676.2	585.4	525.9	494.6	480.0	470.6	452.9	446.6	440.4	442.5	439.3
50°	567.7	499.9	461.2	433.1	423.7	414.3	402.8	396.5	393.4	393.4	392.4
52.5°	487.3	431.0	405.9	379.8	375.7	370.5	357.9	353.8	348.5	347.5	351.7
55°	417.4	378.8	353.8	338.1	333.9	323.5	318.3	313.1	309.9	307.8	308.9
57.5°	356.9	327.7	311.0	297.4	290.1	285.9	276.5	275.5	273.4	273.4	272.4
60°	306.8	285.9	266.1	257.8	252.5	247.3	246.3	240.0	236.9	239.0	237.9
62.5°	259.8	243.1	231.7	222.3	219.1	215.0	211.8	209.8	206.6	207.7	207.7
65°	217.1	203.5	195.1	186.8	185.7	181.6	180.5	178.4	178.4	177.4	179.5
67.5°	178.4	169.1	161.7	156.5	153.4	154.4	150.3	147.1	147.1	146.1	149.2
70°	141.9	136.7	129.4	123.1	119.0	119.0	113.7	112.7	112.7	112.7	111.7
72.5°	109.6	100.2	97.0	95.0	95.0	95.0	92.9	92.9	91.8	92.9	91.8
75°	81.4	80.4	78.3	77.2	77.2	76.2	75.1	75.1	75.1	75.1	75.1
77.5°	63.7	63.7	61.6	60.5	60.5	60.5	59.5	59.5	58.4	58.4	58.4
80°	47.0	47.0	44.9	44.9	44.9	43.8	43.8	43.8	44.9	43.8	43.8
82.5°	32.3	32.3	31.3	32.3	31.3	30.3	30.3	30.3	29.2	30.3	30.3
85°	18.8	18.8	17.7	16.7	17.7	17.7	16.7	17.7	16.7	17.7	16.7
87.5°	7.3	6.3	6.3	6.3	5.2	6.3	5.2	5.2	6.3	5.2	6.3
90°	23.5	24.5	25.5	26.5	27.4	28.4	27.4	28.4	29.4	28.4	29.4
92.5°	136.2	97.0	75.4	65.6	62.2	58.8	56.8	52.9	53.9	51.9	53.9
95°	471.2	352.7	239.0	187.1	169.4	151.8	133.2	124.4	117.6	113.6	117.6
97.5°	923.8	810.2	611.3	482.0	426.2	370.3	304.7	267.4	243.9	233.2	243.9
100°	1120.7	1155.0	1075.7	961.0	891.4	821.9	723.0	651.5	613.3	614.2	613.3
102.5°	1130.5	1269.6	1286.3	1231.4	1193.7	1156.0	1084.5	1031.6	1001.2	972.8	1001.2
105°	1068.8	1273.6	1371.5	1390.1	1377.4	1364.7	1319.6	1282.4	1251.0	1246.1	1251.0
107.5°	980.6	1214.8	1368.6	1445.0	1458.2	1471.4	1465.6	1447.9	1435.2	1424.4	1435.2
110°	898.3	1122.7	1302.9	1426.4	1460.7	1495.0	1522.4	1530.2	1528.3	1526.3	1528.3



TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	826.8	1031.6	1216.7	1358.8	1405.3	1451.8	1507.7	1536.1	1545.9	1546.9	1545.9
115°	772.0	953.2	1123.7	1267.7	1321.1	1374.5	1447.9	1491.0	1510.6	1515.5	1510.6
117.5°	735.7	892.5	1043.3	1175.6	1230.9	1286.3	1362.7	1410.7	1440.1	1447.0	1440.1
120°	708.3	846.4	978.7	1096.2	1145.7	1195.2	1272.6	1327.4	1350.9	1356.8	1350.9
122.5°	685.8	810.2	926.8	1033.5	1078.6	1123.7	1190.3	1238.3	1264.7	1272.6	1264.7
125°	667.1	778.8	885.6	979.7	1018.8	1058.0	1120.7	1163.8	1188.3	1195.2	1188.3
127.5°	649.5	750.4	847.4	933.6	969.8	1006.1	1062.9	1100.2	1122.7	1128.6	1122.7
130°	635.8	724.0	812.1	891.5	924.8	958.1	1010.0	1045.3	1065.9	1073.7	1065.9
132.5°	623.1	699.5	778.8	851.3	882.6	914.0	962.0	997.3	1014.9	1019.8	1014.9
135°	612.3	677.9	747.5	811.2	839.1	867.0	915.0	944.4	962.0	968.9	962.0
137.5°	602.5	657.3	716.1	772.9	797.9	822.9	864.1	894.4	909.1	915.0	909.1
140°	593.7	639.7	689.7	736.7	757.8	778.8	816.1	843.5	859.2	858.2	859.2
142.5°	585.8	623.1	664.2	703.4	721.0	738.7	769.0	792.5	806.3	805.3	806.3
145°	579.0	610.3	642.7	674.0	688.2	702.4	726.9	747.5	755.3	757.3	755.3
147.5°	572.1	599.5	626.0	652.5	662.8	673.0	692.6	707.3	715.1	716.1	715.1
150°	565.3	587.8	610.3	630.9	640.2	649.5	664.2	675.0	680.9	680.9	680.9
152.5°	557.4	577.0	595.6	613.3	620.6	628.0	638.7	648.5	651.5	651.5	651.5
155°	549.6	566.2	581.9	596.6	602.5	608.4	617.2	625.0	627.0	628.0	627.0
157.5°	540.8	554.5	568.2	580.0	584.9	589.8	597.6	603.5	605.4	605.4	605.4
160°	532.0	544.7	555.5	565.3	568.7	572.1	579.0	584.9	584.9	583.9	584.9
162.5°	523.1	532.9	541.7	550.6	553.5	556.4	560.4	565.3	565.3	564.3	565.3
165°	515.3	523.1	529.0	535.9	538.3	540.8	544.7	548.6	547.6	547.6	547.6
167.5°	507.5	514.3	519.2	523.1	525.1	527.1	529.0	532.0	531.0	531.0	531.0
170°	500.6	505.5	508.4	512.4	513.3	514.3	515.3	517.3	516.3	516.3	516.3
172.5°	493.7	497.7	499.6	502.6	503.0	503.5	503.5	505.5	503.5	502.6	503.5
175°	488.8	490.8	491.8	493.7	493.7	493.7	493.7	494.7	493.7	492.8	493.7
177.5°	484.9	485.9	486.9	487.9	487.9	487.9	486.9	487.9	485.9	485.9	485.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1315.9	1309.6	1305.5	1302.3	1299.2	1308.6	1296.1	1282.5	1273.1	1266.9	1264.8
5°	1453.6	1440.1	1428.6	1419.2	1421.3	1421.3	1399.4	1375.4	1354.5	1343.0	1330.5
7.5°	1613.3	1598.7	1575.7	1570.5	1566.3	1540.3	1518.3	1474.5	1448.4	1422.3	1399.4
10°	1771.9	1753.1	1731.2	1723.9	1713.5	1681.1	1647.7	1591.4	1559.0	1511.0	1480.8
12.5°	1920.1	1897.1	1875.2	1870.0	1854.4	1826.2	1768.8	1710.4	1655.0	1603.9	1550.7
15°	2044.3	2038.0	2004.6	1983.8	1949.3	1910.7	1898.2	1818.9	1749.0	1695.7	1599.7
17.5°	2148.6	2119.4	2088.1	2074.5	2061.0	2016.1	1971.2	1889.8	1814.7	1736.4	1674.9
20°	2232.1	2199.8	2177.9	2158.0	2151.8	2100.6	2029.7	1957.7	1875.2	1787.6	1707.2
22.5°	2236.3	2232.1	2217.5	2206.0	2193.5	2160.1	2103.8	2014.0	1926.4	1830.4	1725.0
25°	2149.7	2143.4	2185.2	2174.7	2183.1	2170.6	2140.3	2065.2	1962.9	1850.2	1743.7
27.5°	1888.8	1952.5	2018.2	2041.2	2056.8	2101.7	2116.3	2074.5	1992.1	1872.1	1753.1
30°	1534.0	1618.5	1725.0	1782.4	1826.2	1909.7	2018.2	2031.8	1993.2	1897.1	1751.1
32.5°	1204.2	1281.5	1367.0	1434.9	1493.3	1664.4	1810.5	1915.9	1934.7	1884.6	1756.3
35°	970.5	1003.9	1085.3	1150.0	1229.3	1375.4	1547.6	1717.7	1832.4	1838.7	1740.6
37.5°	800.4	818.1	889.1	925.6	972.6	1100.9	1261.6	1483.9	1662.4	1746.9	1696.8
40°	662.6	703.3	744.0	764.9	798.3	887.0	1041.4	1215.7	1436.9	1593.5	1629.0
42.5°	575.0	592.7	618.8	648.0	668.9	746.1	849.4	1009.1	1208.4	1426.5	1524.6
45°	507.2	513.4	540.6	559.3	581.2	635.5	708.6	842.1	1017.4	1232.4	1399.4
47.5°	450.8	463.3	477.9	489.4	504.0	545.8	608.4	705.4	859.9	1051.9	1231.4
50°	400.7	408.0	426.8	432.0	442.5	471.7	519.7	593.8	721.1	874.5	1060.2
52.5°	353.8	367.3	374.6	381.9	391.3	415.3	446.6	507.2	603.2	747.2	904.7
55°	317.2	321.4	331.8	338.1	345.4	362.1	389.2	434.1	509.2	624.0	773.3
57.5°	281.8	281.8	292.2	297.4	304.7	317.2	341.2	375.7	429.9	515.5	652.2
60°	244.2	245.2	253.6	259.8	261.9	274.4	294.3	321.4	363.2	425.8	537.4
62.5°	210.8	216.0	220.2	222.3	229.6	236.9	253.6	272.4	301.6	356.9	436.2
65°	182.6	183.7	186.8	188.9	192.0	200.4	212.9	225.4	250.4	291.1	355.8
67.5°	150.3	154.4	158.6	158.6	161.7	165.9	178.4	188.9	207.7	231.7	275.5
70°	112.7	114.8	121.1	124.2	128.4	135.7	141.9	148.2	162.8	180.5	213.9
72.5°	93.9	93.9	96.0	97.0	97.0	102.3	111.7	117.9	125.2	137.7	160.7
75°	75.1	75.1	78.3	77.2	79.3	81.4	82.4	86.6	90.8	100.2	113.7
77.5°	59.5	60.5	60.5	61.6	61.6	62.6	63.7	65.7	67.8	73.0	79.3
80°	43.8	44.9	44.9	45.9	45.9	47.0	48.0	49.0	51.1	53.2	56.4
82.5°	30.3	31.3	31.3	32.3	31.3	32.3	33.4	33.4	34.4	36.5	37.6
85°	17.7	17.7	18.8	17.7	17.7	17.7	18.8	18.8	19.8	23.0	23.0
87.5°	5.2	6.3	5.2	6.3	6.3	6.3	6.3	7.3	7.3	8.3	9.4
90°	28.4	27.4	28.4	27.4	26.5	25.5	24.5	23.5	24.5	21.6	18.6
92.5°	52.9	56.8	58.8	62.2	65.6	75.4	97.0	136.2	182.2	201.8	150.9
95°	124.4	133.2	151.8	169.4	187.1	239.0	352.7	471.2	580.9	517.3	356.6
97.5°	267.4	304.7	370.3	426.2	482.0	611.3	810.2	923.8	893.4	667.1	396.8
100°	651.5	723.0	821.9	891.4	961.0	1075.7	1155.0	1120.7	927.7	627.0	369.3
102.5°	1031.6	1084.5	1156.0	1193.7	1231.4	1286.3	1269.6	1130.5	864.1	568.2	345.8
105°	1282.4	1319.6	1364.7	1377.4	1390.1	1371.5	1273.6	1068.8	787.6	522.2	337.0
107.5°	1447.9	1465.6	1471.4	1458.2	1445.0	1368.6	1214.8	980.6	720.0	488.8	335.0
110°	1530.2	1522.4	1495.0	1460.7	1426.4	1302.9	1122.7	898.3	664.2	471.2	339.9

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1536.1	1507.7	1451.8	1405.3	1358.8	1216.7	1031.6	826.8	627.0	461.4	349.7
115°	1491.0	1447.9	1374.5	1321.1	1267.7	1123.7	953.2	772.0	602.5	460.4	360.5
117.5°	1410.7	1362.7	1286.3	1230.9	1175.6	1043.3	892.5	735.7	585.8	461.4	374.2
120°	1327.4	1272.6	1195.2	1145.7	1096.2	978.7	846.4	708.3	575.1	465.3	389.9
122.5°	1238.3	1190.3	1123.7	1078.6	1033.5	926.8	810.2	685.8	568.2	472.2	404.6
125°	1163.8	1120.7	1058.0	1018.8	979.7	885.6	778.8	667.1	562.3	479.1	420.3
127.5°	1100.2	1062.9	1006.1	969.8	933.6	847.4	750.4	649.5	559.4	486.9	433.0
130°	1045.3	1010.0	958.1	924.8	891.5	812.1	724.0	635.8	556.4	494.7	445.7
132.5°	997.3	962.0	914.0	882.6	851.3	778.8	699.5	623.1	555.5	500.6	457.5
135°	944.4	915.0	867.0	839.1	811.2	747.5	677.9	612.3	554.5	506.5	467.3
137.5°	894.4	864.1	822.9	797.9	772.9	716.1	657.3	602.5	552.5	510.4	475.1
140°	843.5	816.1	778.8	757.8	736.7	689.7	639.7	593.7	551.5	514.3	481.0
142.5°	792.5	769.0	738.7	721.0	703.4	664.2	623.1	585.8	549.6	517.3	486.9
145°	747.5	726.9	702.4	688.2	674.0	642.7	610.3	579.0	547.6	518.2	490.8
147.5°	707.3	692.6	673.0	662.8	652.5	626.0	599.5	572.1	544.7	518.2	493.7
150°	675.0	664.2	649.5	640.2	630.9	610.3	587.8	565.3	540.8	518.2	494.7
152.5°	648.5	638.7	628.0	620.6	613.3	595.6	577.0	557.4	535.9	515.3	496.7
155°	625.0	617.2	608.4	602.5	596.6	581.9	566.2	549.6	530.0	513.3	496.7
157.5°	603.5	597.6	589.8	584.9	580.0	568.2	554.5	540.8	525.1	510.4	497.7
160°	584.9	579.0	572.1	568.7	565.3	555.5	544.7	532.0	519.2	508.4	497.7
162.5°	565.3	560.4	556.4	553.5	550.6	541.7	532.9	523.1	513.3	504.5	496.7
165°	548.6	544.7	540.8	538.3	535.9	529.0	523.1	515.3	507.5	500.6	494.7
167.5°	532.0	529.0	527.1	525.1	523.1	519.2	514.3	507.5	501.6	496.7	493.7
170°	517.3	515.3	514.3	513.3	512.4	508.4	505.5	500.6	495.7	492.8	490.8
172.5°	505.5	503.5	503.5	503.0	502.6	499.6	497.7	493.7	490.8	489.8	489.8
175°	494.7	493.7	493.7	493.7	493.7	491.8	490.8	488.8	486.9	486.9	487.9
177.5°	487.9	486.9	487.9	487.9	487.9	486.9	485.9	484.9	483.9	484.9	486.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1261.6	1256.4	1251.2	1251.2	1239.7	1229.3	1224.1	1226.2	1219.9	1211.5	1203.2
5°	1316.9	1296.1	1291.9	1280.4	1264.8	1242.8	1231.4	1220.9	1208.4	1191.7	1176.1
7.5°	1368.1	1340.9	1326.3	1314.9	1284.6	1254.3	1229.3	1212.6	1190.7	1165.6	1146.8
10°	1434.9	1384.8	1369.1	1343.0	1300.2	1257.5	1228.2	1201.1	1170.8	1141.6	1116.6
12.5°	1488.1	1430.7	1401.5	1375.4	1320.1	1265.8	1216.8	1183.4	1146.8	1114.5	1082.1
15°	1548.6	1483.9	1432.8	1401.5	1331.6	1265.8	1210.5	1163.5	1122.8	1083.2	1055.0
17.5°	1577.8	1496.4	1473.5	1428.6	1327.4	1261.6	1193.8	1143.7	1094.7	1048.8	1015.4
20°	1623.7	1528.8	1471.4	1441.1	1351.4	1254.3	1175.0	1117.6	1066.5	1017.4	982.0
22.5°	1626.9	1523.6	1486.0	1428.6	1318.0	1232.4	1158.3	1088.4	1028.9	983.0	946.5
25°	1619.6	1514.2	1462.0	1416.1	1324.2	1219.9	1124.9	1056.1	997.6	944.4	901.6
27.5°	1616.4	1487.0	1438.0	1392.1	1288.8	1183.4	1105.1	1026.8	960.1	913.1	869.3
30°	1612.3	1457.8	1398.3	1345.1	1250.2	1155.2	1061.3	993.4	929.8	870.3	826.5
32.5°	1585.1	1418.2	1357.6	1301.3	1199.0	1104.1	1030.0	958.0	889.1	833.8	794.1
35°	1576.8	1381.6	1302.3	1241.8	1141.6	1057.1	978.8	919.4	854.7	799.3	752.4
37.5°	1552.8	1344.1	1258.5	1181.3	1076.9	996.6	939.2	879.7	817.1	757.6	720.0
40°	1511.0	1300.2	1203.2	1123.9	1016.4	935.0	881.8	838.0	776.4	723.2	677.3
42.5°	1449.5	1255.4	1151.0	1067.5	948.6	872.4	828.6	786.8	734.6	679.3	641.8
45°	1378.5	1195.9	1098.8	1006.0	884.9	810.8	764.9	739.9	691.9	644.9	601.1
47.5°	1281.5	1134.3	1038.3	942.3	819.2	747.2	710.6	685.6	652.2	601.1	565.6
50°	1159.4	1055.0	964.2	878.7	754.5	685.6	649.1	630.3	602.1	565.6	531.2
52.5°	1023.7	963.2	888.0	808.7	688.7	624.0	590.6	576.0	555.2	520.7	491.5
55°	887.0	860.9	809.8	731.5	619.9	566.6	537.4	518.6	503.0	477.9	452.9
57.5°	764.9	752.4	716.9	656.4	562.5	507.2	482.1	469.6	457.1	438.3	413.2
60°	638.6	652.2	615.7	585.4	499.9	451.9	429.9	416.4	410.1	393.4	377.8
62.5°	529.1	541.6	520.7	497.8	437.2	394.5	380.9	368.4	364.2	349.6	333.9
65°	429.9	445.6	429.9	417.4	380.9	345.4	328.7	322.5	318.3	308.9	296.4
67.5°	342.3	357.9	350.6	335.0	323.5	294.3	284.9	278.6	276.5	269.2	258.8
70°	257.8	279.7	281.8	272.4	261.9	248.4	242.1	240.0	234.8	228.5	222.3
72.5°	185.7	210.8	211.8	211.8	205.6	205.6	199.3	196.2	196.2	189.9	182.6
75°	136.7	153.4	155.5	157.6	160.7	163.8	159.7	159.7	158.6	152.4	149.2
77.5°	90.8	105.4	110.6	117.9	122.1	122.1	124.2	126.3	124.2	121.1	119.0
80°	58.4	68.9	75.1	79.3	85.6	88.7	91.8	92.9	90.8	89.7	86.6
82.5°	38.6	41.7	44.9	50.1	57.4	62.6	62.6	61.6	63.7	62.6	61.6
85°	21.9	24.0	25.0	26.1	30.3	35.5	36.5	37.6	39.7	37.6	35.5
87.5°	8.3	9.4	9.4	9.4	11.5	12.5	15.7	19.8	18.8	16.7	16.7
90°	15.7	12.7	11.8	10.8	8.8	5.9	3.9	2.0	3.9	5.9	8.8
92.5°	98.9	67.6	58.8	50.0	40.2	31.3	21.6	14.7	21.6	31.3	40.2
95°	210.6	127.4	108.2	89.1	63.7	47.0	36.2	33.3	36.2	47.0	63.7
97.5°	227.3	145.0	124.0	102.9	77.4	62.7	53.9	52.9	53.9	62.7	77.4
100°	224.3	155.8	136.7	117.6	94.0	80.3	73.5	72.5	73.5	80.3	94.0
102.5°	228.3	168.5	151.4	134.2	113.6	100.9	95.0	93.1	95.0	100.9	113.6
105°	236.1	183.2	168.0	152.8	134.2	122.5	116.6	113.6	116.6	122.5	134.2
107.5°	248.8	201.8	187.6	173.4	155.8	144.0	138.1	135.2	138.1	144.0	155.8
110°	265.5	221.4	207.7	194.0	177.3	166.5	161.6	158.7	161.6	166.5	177.3

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	282.1	242.0	228.8	215.5	198.9	188.1	183.2	180.3	183.2	188.1	198.9
115°	300.8	263.5	250.3	237.1	220.4	210.6	204.7	200.8	204.7	210.6	220.4
117.5°	320.3	283.1	270.8	258.6	240.0	231.2	226.3	221.4	226.3	231.2	240.0
120°	339.0	303.7	291.4	279.2	260.6	250.8	245.9	243.0	245.9	250.8	260.6
122.5°	358.6	324.3	311.0	297.8	280.2	269.4	264.5	261.6	264.5	269.4	280.2
125°	377.2	342.9	329.6	316.4	297.8	287.0	281.2	279.2	281.2	287.0	297.8
127.5°	393.8	360.5	347.3	334.1	313.5	302.7	295.9	292.9	295.9	302.7	313.5
130°	408.5	376.2	363.0	349.7	329.2	317.4	308.6	305.7	308.6	317.4	329.2
132.5°	421.3	389.9	377.2	364.4	343.9	329.2	319.4	315.4	319.4	329.2	343.9
135°	434.0	403.6	390.4	377.2	356.6	341.9	331.1	327.2	331.1	341.9	356.6
137.5°	442.8	413.4	401.2	388.9	368.4	352.7	341.9	338.0	341.9	352.7	368.4
140°	451.6	423.2	411.0	398.7	379.1	363.5	353.7	348.8	353.7	363.5	379.1
142.5°	458.5	431.0	419.8	408.5	388.9	375.2	364.4	360.5	364.4	375.2	388.9
145°	464.4	438.9	427.6	416.4	399.7	385.0	376.2	373.2	376.2	385.0	399.7
147.5°	469.3	445.7	436.0	426.2	409.5	396.8	387.9	386.0	387.9	396.8	409.5
150°	474.2	451.6	442.8	434.0	420.3	407.5	399.7	398.7	399.7	407.5	420.3
152.5°	477.1	458.5	450.2	441.8	430.1	419.3	411.5	411.5	411.5	419.3	430.1
155°	481.0	464.4	457.5	450.6	439.9	430.1	424.2	424.2	424.2	430.1	439.9
157.5°	483.0	469.3	463.9	458.5	448.7	439.9	435.0	434.0	435.0	439.9	448.7
160°	485.9	474.2	469.3	464.4	457.5	449.7	445.7	445.7	445.7	449.7	457.5
162.5°	486.9	477.1	473.2	469.3	463.4	457.5	454.6	454.6	454.6	457.5	463.4
165°	487.9	480.0	476.6	473.2	469.3	464.4	462.4	463.4	462.4	464.4	469.3
167.5°	487.9	482.0	479.6	477.1	474.2	470.2	469.3	470.2	469.3	470.2	474.2
170°	486.9	482.0	481.0	480.0	478.1	475.1	474.2	476.1	474.2	475.1	478.1
172.5°	486.9	483.0	482.5	482.0	481.0	479.1	479.1	480.0	479.1	479.1	481.0
175°	485.9	483.9	483.4	483.0	483.0	481.0	482.0	483.0	482.0	481.0	483.0
177.5°	484.9	483.9	483.9	483.9	483.9	483.0	483.9	484.9	483.9	483.0	483.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1203.2	1198.0	1195.9	1190.7	1178.2	1169.8	1160.4	1154.1	1155.2	1150.0	1153.1
5°	1165.6	1164.6	1157.3	1146.8	1129.1	1119.7	1103.0	1094.7	1090.5	1091.5	1085.3
7.5°	1134.3	1124.9	1119.7	1103.0	1086.3	1066.5	1052.9	1045.6	1039.4	1033.1	1028.9
10°	1098.8	1090.5	1082.1	1064.4	1041.4	1022.7	1003.9	996.6	987.2	983.0	979.9
12.5°	1061.3	1056.1	1045.6	1024.8	998.7	980.9	959.0	954.8	942.3	934.0	931.9
15°	1026.8	1023.7	1004.9	980.9	954.8	937.1	918.3	905.8	884.9	889.1	881.8
17.5°	990.3	976.7	965.3	932.9	920.4	893.3	871.4	865.1	850.5	841.1	831.7
20°	949.6	941.3	926.7	905.8	875.5	844.2	827.5	817.1	808.7	794.1	790.0
22.5°	911.0	900.6	888.0	860.9	834.8	808.7	785.8	776.4	766.0	755.5	749.3
25°	880.7	865.1	851.5	818.1	792.0	770.1	755.5	739.9	725.3	719.0	716.9
27.5°	833.8	824.4	810.8	779.5	755.5	731.5	718.0	707.5	691.9	684.6	678.3
30°	803.5	784.7	769.1	744.0	720.0	694.0	681.4	668.9	659.5	650.1	642.8
32.5°	762.8	748.2	735.7	710.6	686.6	662.6	649.1	630.3	625.1	617.8	609.4
35°	723.2	713.8	700.2	673.1	647.0	630.3	615.7	597.9	591.7	586.5	579.2
37.5°	685.6	672.0	662.6	636.6	613.6	593.8	582.3	567.7	563.5	557.2	552.0
40°	653.3	639.7	630.3	604.2	580.2	559.3	552.0	537.4	531.2	523.9	520.7
42.5°	616.7	605.3	592.7	573.9	548.9	528.0	513.4	505.1	496.7	493.6	487.3
45°	578.1	567.7	558.3	537.4	511.3	496.7	484.2	472.7	466.5	461.2	457.1
47.5°	544.7	535.3	522.8	499.9	479.0	465.4	452.9	441.4	435.2	428.9	423.7
50°	506.1	500.9	487.3	465.4	445.6	429.9	418.5	408.0	403.8	396.5	388.2
52.5°	471.7	462.3	450.8	433.1	415.3	396.5	380.9	374.6	367.3	363.2	355.8
55°	431.0	424.7	412.2	396.5	377.8	362.1	350.6	342.3	332.9	328.7	319.3
57.5°	396.5	385.1	378.8	359.0	341.2	325.6	317.2	308.9	298.5	292.2	288.0
60°	359.0	348.5	339.1	322.5	309.9	293.2	280.7	273.4	266.1	257.8	253.6
62.5°	322.5	314.1	302.6	289.1	273.4	259.8	250.4	240.0	235.8	227.5	224.4
65°	282.8	276.5	267.1	251.5	239.0	227.5	218.1	209.8	205.6	202.4	200.4
67.5°	247.3	239.0	232.7	219.1	205.6	196.2	191.0	185.7	180.5	177.4	174.3
70°	210.8	204.5	198.3	185.7	176.4	168.0	163.8	159.7	156.5	153.4	150.3
72.5°	173.2	170.1	163.8	155.5	148.2	141.9	138.8	133.6	130.4	125.2	123.1
75°	143.0	137.7	134.6	127.3	121.1	115.8	111.7	105.4	101.2	99.1	98.1
77.5°	112.7	110.6	106.4	100.2	97.0	91.8	85.6	83.5	81.4	81.4	80.4
80°	84.5	81.4	78.3	73.0	69.9	65.7	65.7	65.7	64.7	65.7	64.7
82.5°	57.4	55.3	53.2	50.1	49.0	49.0	50.1	50.1	50.1	50.1	50.1
85°	33.4	33.4	33.4	34.4	33.4	33.4	34.4	35.5	34.4	34.4	33.4
87.5°	15.7	15.7	16.7	16.7	17.7	17.7	17.7	17.7	17.7	17.7	18.8
90°	10.8	11.8	12.7	15.7	18.6	21.6	24.5	23.5	24.5	25.5	26.5
92.5°	50.0	58.8	67.6	98.9	150.9	201.8	182.2	136.2	97.0	75.4	65.6
95°	89.1	108.2	127.4	210.6	356.6	517.3	580.9	471.2	352.7	239.0	187.1
97.5°	102.9	124.0	145.0	227.3	396.8	667.1	893.4	923.8	810.2	611.3	482.0
100°	117.6	136.7	155.8	224.3	369.3	627.0	927.7	1120.7	1155.0	1075.7	961.0
102.5°	134.2	151.4	168.5	228.3	345.8	568.2	864.1	1130.5	1269.6	1286.3	1231.4
105°	152.8	168.0	183.2	236.1	337.0	522.2	787.6	1068.8	1273.6	1371.5	1390.1
107.5°	173.4	187.6	201.8	248.8	335.0	488.8	720.0	980.6	1214.8	1368.6	1445.0
110°	194.0	207.7	221.4	265.5	339.9	471.2	664.2	898.3	1122.7	1302.9	1426.4

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	215.5	228.8	242.0	282.1	349.7	461.4	627.0	826.8	1031.6	1216.7	1358.8
115°	237.1	250.3	263.5	300.8	360.5	460.4	602.5	772.0	953.2	1123.7	1267.7
117.5°	258.6	270.8	283.1	320.3	374.2	461.4	585.8	735.7	892.5	1043.3	1175.6
120°	279.2	291.4	303.7	339.0	389.9	465.3	575.1	708.3	846.4	978.7	1096.2
122.5°	297.8	311.0	324.3	358.6	404.6	472.2	568.2	685.8	810.2	926.8	1033.5
125°	316.4	329.6	342.9	377.2	420.3	479.1	562.3	667.1	778.8	885.6	979.7
127.5°	334.1	347.3	360.5	393.8	433.0	486.9	559.4	649.5	750.4	847.4	933.6
130°	349.7	363.0	376.2	408.5	445.7	494.7	556.4	635.8	724.0	812.1	891.5
132.5°	364.4	377.2	389.9	421.3	457.5	500.6	555.5	623.1	699.5	778.8	851.3
135°	377.2	390.4	403.6	434.0	467.3	506.5	554.5	612.3	677.9	747.5	811.2
137.5°	388.9	401.2	413.4	442.8	475.1	510.4	552.5	602.5	657.3	716.1	772.9
140°	398.7	411.0	423.2	451.6	481.0	514.3	551.5	593.7	639.7	689.7	736.7
142.5°	408.5	419.8	431.0	458.5	486.9	517.3	549.6	585.8	623.1	664.2	703.4
145°	416.4	427.6	438.9	464.4	490.8	518.2	547.6	579.0	610.3	642.7	674.0
147.5°	426.2	436.0	445.7	469.3	493.7	518.2	544.7	572.1	599.5	626.0	652.5
150°	434.0	442.8	451.6	474.2	494.7	518.2	540.8	565.3	587.8	610.3	630.9
152.5°	441.8	450.2	458.5	477.1	496.7	515.3	535.9	557.4	577.0	595.6	613.3
155°	450.6	457.5	464.4	481.0	496.7	513.3	530.0	549.6	566.2	581.9	596.6
157.5°	458.5	463.9	469.3	483.0	497.7	510.4	525.1	540.8	554.5	568.2	580.0
160°	464.4	469.3	474.2	485.9	497.7	508.4	519.2	532.0	544.7	555.5	565.3
162.5°	469.3	473.2	477.1	486.9	496.7	504.5	513.3	523.1	532.9	541.7	550.6
165°	473.2	476.6	480.0	487.9	494.7	500.6	507.5	515.3	523.1	529.0	535.9
167.5°	477.1	479.6	482.0	487.9	493.7	496.7	501.6	507.5	514.3	519.2	523.1
170°	480.0	481.0	482.0	486.9	490.8	492.8	495.7	500.6	505.5	508.4	512.4
172.5°	482.0	482.5	483.0	486.9	489.8	489.8	490.8	493.7	497.7	499.6	502.6
175°	483.0	483.4	483.9	485.9	487.9	486.9	486.9	488.8	490.8	491.8	493.7
177.5°	483.9	483.9	483.9	484.9	486.9	484.9	483.9	484.9	485.9	486.9	487.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1152.1	1153.1	1150.0	1143.7	1142.7	1144.8	1151.0	1148.9	1143.7	1153.1	1144.8
5°	1088.4	1083.2	1081.1	1083.2	1076.9	1073.8	1080.1	1076.9	1080.1	1081.1	1084.2
7.5°	1026.8	1027.9	1021.6	1022.7	1014.3	1016.4	1016.4	1016.4	1019.5	1021.6	1025.8
10°	973.6	975.7	968.4	969.4	963.2	959.0	962.1	968.4	968.4	968.4	970.5
12.5°	930.8	921.4	916.2	915.2	907.9	905.8	912.0	914.1	919.4	919.4	922.5
15°	877.6	875.5	871.4	871.4	853.6	857.8	859.9	867.2	877.6	869.3	871.4
17.5°	829.6	824.4	819.2	817.1	815.0	808.7	817.1	816.0	822.3	823.3	826.5
20°	786.8	782.7	772.2	773.3	775.3	766.0	771.2	771.2	777.4	783.7	791.0
22.5°	745.1	740.9	735.7	737.8	731.5	729.4	729.4	734.6	742.0	747.2	746.1
25°	712.7	705.4	702.3	699.2	696.0	698.1	695.0	700.2	705.4	708.6	705.4
27.5°	676.2	673.1	666.8	663.7	658.5	660.6	662.6	666.8	669.9	669.9	673.1
30°	640.7	636.6	634.5	631.3	631.3	627.2	628.2	632.4	635.5	638.6	642.8
32.5°	606.3	603.2	600.0	600.0	597.9	596.9	595.9	602.1	602.1	608.4	608.4
35°	578.1	572.9	572.9	567.7	569.8	568.7	566.6	570.8	571.9	576.0	575.0
37.5°	546.8	546.8	544.7	539.5	535.3	536.4	541.6	541.6	544.7	543.7	546.8
40°	515.5	513.4	513.4	510.3	509.2	508.2	509.2	510.3	515.5	514.5	515.5
42.5°	484.2	485.2	480.0	480.0	480.0	476.9	477.9	479.0	481.1	483.2	486.3
45°	453.9	451.9	450.8	448.7	446.6	447.7	446.6	450.8	449.8	451.9	455.0
47.5°	421.6	418.5	417.4	413.2	413.2	415.3	414.3	417.4	418.5	421.6	419.5
50°	390.3	386.1	383.0	384.0	377.8	379.8	379.8	383.0	386.1	387.2	389.2
52.5°	353.8	352.7	351.7	346.5	345.4	344.4	345.4	346.5	350.6	353.8	354.8
55°	318.3	317.2	311.0	308.9	305.8	305.8	307.8	308.9	316.2	317.2	321.4
57.5°	285.9	282.8	275.5	274.4	274.4	274.4	271.3	275.5	277.6	282.8	282.8
60°	250.4	250.4	244.2	244.2	245.2	244.2	244.2	245.2	245.2	249.4	251.5
62.5°	222.3	221.2	221.2	219.1	218.1	219.1	218.1	218.1	219.1	222.3	225.4
65°	197.2	196.2	195.1	194.1	192.0	192.0	193.1	195.1	195.1	197.2	198.3
67.5°	173.2	173.2	171.1	171.1	170.1	169.1	170.1	169.1	173.2	173.2	174.3
70°	149.2	148.2	145.1	144.0	140.9	141.9	141.9	145.1	146.1	148.2	150.3
72.5°	120.0	120.0	117.9	115.8	116.9	114.8	114.8	115.8	115.8	119.0	120.0
75°	99.1	97.0	96.0	97.0	96.0	98.1	96.0	96.0	98.1	98.1	98.1
77.5°	81.4	81.4	80.4	80.4	81.4	80.4	81.4	81.4	81.4	80.4	81.4
80°	66.8	65.7	65.7	65.7	64.7	64.7	64.7	64.7	64.7	64.7	64.7
82.5°	50.1	50.1	49.0	50.1	50.1	49.0	50.1	49.0	49.0	50.1	50.1
85°	33.4	35.5	33.4	33.4	34.4	34.4	35.5	34.4	35.5	33.4	34.4
87.5°	17.7	18.8	18.8	17.7	17.7	18.8	18.8	18.8	19.8	17.7	18.8
90°	27.4	28.4	27.4	28.4	29.4	28.4	29.4	28.4	27.4	28.4	27.4
92.5°	62.2	58.8	56.8	52.9	53.9	51.9	53.9	52.9	56.8	58.8	62.2
95°	169.4	151.8	133.2	124.4	117.6	113.6	117.6	124.4	133.2	151.8	169.4
97.5°	426.2	370.3	304.7	267.4	243.9	233.2	243.9	267.4	304.7	370.3	426.2
100°	891.4	821.9	723.0	651.5	613.3	614.2	613.3	651.5	723.0	821.9	891.4
102.5°	1193.7	1156.0	1084.5	1031.6	1001.2	972.8	1001.2	1031.6	1084.5	1156.0	1193.7
105°	1377.4	1364.7	1319.6	1282.4	1251.0	1246.1	1251.0	1282.4	1319.6	1364.7	1377.4
107.5°	1458.2	1471.4	1465.6	1447.9	1435.2	1424.4	1435.2	1447.9	1465.6	1471.4	1458.2
110°	1460.7	1495.0	1522.4	1530.2	1528.3	1526.3	1528.3	1530.2	1522.4	1495.0	1460.7

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1405.3	1451.8	1507.7	1536.1	1545.9	1546.9	1545.9	1536.1	1507.7	1451.8	1405.3
115°	1321.1	1374.5	1447.9	1491.0	1510.6	1515.5	1510.6	1491.0	1447.9	1374.5	1321.1
117.5°	1230.9	1286.3	1362.7	1410.7	1440.1	1447.0	1440.1	1410.7	1362.7	1286.3	1230.9
120°	1145.7	1195.2	1272.6	1327.4	1350.9	1356.8	1350.9	1327.4	1272.6	1195.2	1145.7
122.5°	1078.6	1123.7	1190.3	1238.3	1264.7	1272.6	1264.7	1238.3	1190.3	1123.7	1078.6
125°	1018.8	1058.0	1120.7	1163.8	1188.3	1195.2	1188.3	1163.8	1120.7	1058.0	1018.8
127.5°	969.8	1006.1	1062.9	1100.2	1122.7	1128.6	1122.7	1100.2	1062.9	1006.1	969.8
130°	924.8	958.1	1010.0	1045.3	1065.9	1073.7	1065.9	1045.3	1010.0	958.1	924.8
132.5°	882.6	914.0	962.0	997.3	1014.9	1019.8	1014.9	997.3	962.0	914.0	882.6
135°	839.1	867.0	915.0	944.4	962.0	968.9	962.0	944.4	915.0	867.0	839.1
137.5°	797.9	822.9	864.1	894.4	909.1	915.0	909.1	894.4	864.1	822.9	797.9
140°	757.8	778.8	816.1	843.5	859.2	858.2	859.2	843.5	816.1	778.8	757.8
142.5°	721.0	738.7	769.0	792.5	806.3	805.3	806.3	792.5	769.0	738.7	721.0
145°	688.2	702.4	726.9	747.5	755.3	757.3	755.3	747.5	726.9	702.4	688.2
147.5°	662.8	673.0	692.6	707.3	715.1	716.1	715.1	707.3	692.6	673.0	662.8
150°	640.2	649.5	664.2	675.0	680.9	680.9	680.9	675.0	664.2	649.5	640.2
152.5°	620.6	628.0	638.7	648.5	651.5	651.5	651.5	648.5	638.7	628.0	620.6
155°	602.5	608.4	617.2	625.0	627.0	628.0	627.0	625.0	617.2	608.4	602.5
157.5°	584.9	589.8	597.6	603.5	605.4	605.4	605.4	603.5	597.6	589.8	584.9
160°	568.7	572.1	579.0	584.9	584.9	583.9	584.9	584.9	579.0	572.1	568.7
162.5°	553.5	556.4	560.4	565.3	565.3	564.3	565.3	565.3	560.4	556.4	553.5
165°	538.3	540.8	544.7	548.6	547.6	547.6	547.6	548.6	544.7	540.8	538.3
167.5°	525.1	527.1	529.0	532.0	531.0	531.0	531.0	532.0	529.0	527.1	525.1
170°	513.3	514.3	515.3	517.3	516.3	516.3	516.3	517.3	515.3	514.3	513.3
172.5°	503.0	503.5	503.5	505.5	503.5	502.6	503.5	505.5	503.5	503.5	503.0
175°	493.7	493.7	493.7	494.7	493.7	492.8	493.7	494.7	493.7	493.7	493.7
177.5°	487.9	487.9	486.9	487.9	485.9	485.9	485.9	487.9	486.9	487.9	487.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1153.1	1157.3	1153.1	1144.8	1153.1	1158.3	1163.5	1171.9	1176.1	1176.1	1182.3
5°	1087.4	1095.7	1092.6	1090.5	1098.8	1104.1	1112.4	1122.8	1134.3	1141.6	1150.0
7.5°	1028.9	1034.1	1039.4	1039.4	1047.7	1059.2	1071.7	1084.2	1098.8	1109.3	1115.5
10°	977.8	982.0	985.1	989.3	1001.8	1014.3	1031.0	1046.7	1059.2	1070.7	1081.1
12.5°	928.7	935.0	942.3	945.4	954.8	970.5	986.1	1004.9	1024.8	1036.2	1046.7
15°	881.8	884.9	893.3	902.7	911.0	927.7	947.5	967.4	984.1	1001.8	1011.2
17.5°	833.8	834.8	856.7	851.5	878.7	894.3	904.7	923.5	950.7	965.3	979.9
20°	786.8	797.3	806.7	811.9	826.5	844.2	874.5	889.1	911.0	924.6	937.1
22.5°	750.3	766.0	766.0	778.5	785.8	802.5	824.4	852.6	876.6	886.0	903.7
25°	718.0	725.3	737.8	742.0	755.5	770.1	784.7	815.0	841.1	853.6	866.1
27.5°	676.2	685.6	702.3	702.3	720.0	735.7	753.4	773.3	799.3	817.1	830.7
30°	643.9	653.3	660.6	672.0	679.3	694.0	725.3	739.9	762.8	778.5	795.2
32.5°	613.6	620.9	627.2	639.7	648.0	664.7	681.4	707.5	727.3	742.0	759.7
35°	580.2	587.5	595.9	605.3	617.8	633.4	649.1	671.0	690.8	704.4	719.0
37.5°	548.9	554.1	566.6	572.9	583.3	597.9	617.8	640.7	658.5	668.9	683.5
40°	518.6	522.8	532.2	543.7	551.0	562.5	583.3	603.2	625.1	637.6	649.1
42.5°	486.3	491.5	499.9	511.3	522.8	535.3	546.8	569.8	589.6	600.0	612.6
45°	458.1	461.2	467.5	479.0	490.5	499.9	517.6	538.5	557.2	565.6	579.2
47.5°	424.7	427.8	437.2	442.5	455.0	467.5	485.2	506.1	522.8	531.2	543.7
50°	390.3	393.4	399.7	411.2	419.5	433.1	448.7	466.5	487.3	498.8	506.1
52.5°	356.9	363.2	368.4	377.8	388.2	401.8	416.4	433.1	450.8	462.3	470.6
55°	323.5	328.7	335.0	340.2	352.7	365.2	381.9	397.6	413.2	423.7	433.1
57.5°	285.9	293.2	299.5	309.9	319.3	329.8	348.5	361.1	379.8	387.2	395.5
60°	253.6	260.9	266.1	274.4	282.8	296.4	308.9	324.5	340.2	349.6	360.0
62.5°	226.4	229.6	232.7	241.1	249.4	261.9	274.4	290.1	306.8	312.0	320.4
65°	199.3	202.4	207.7	215.0	221.2	228.5	242.1	254.6	270.3	278.6	281.8
67.5°	176.4	179.5	180.5	185.7	191.0	199.3	206.6	219.1	233.8	239.0	245.2
70°	150.3	155.5	156.5	160.7	162.8	168.0	176.4	185.7	197.2	206.6	211.8
72.5°	120.0	127.3	129.4	135.7	138.8	144.0	150.3	157.6	164.9	169.1	173.2
75°	98.1	100.2	101.2	106.4	111.7	119.0	122.1	126.3	132.5	137.7	141.9
77.5°	81.4	82.4	83.5	83.5	84.5	88.7	95.0	100.2	104.4	106.4	109.6
80°	65.7	64.7	64.7	65.7	65.7	65.7	67.8	75.1	77.2	82.4	81.4
82.5°	51.1	49.0	50.1	49.0	49.0	49.0	49.0	50.1	50.1	53.2	55.3
85°	33.4	34.4	33.4	33.4	32.3	33.4	32.3	32.3	31.3	31.3	30.3
87.5°	17.7	18.8	17.7	17.7	16.7	17.7	16.7	16.7	15.7	15.7	13.6
90°	26.5	25.5	24.5	23.5	24.5	21.6	18.6	15.7	12.7	11.8	10.8
92.5°	65.6	75.4	97.0	136.2	182.2	201.8	150.9	98.9	67.6	58.8	50.0
95°	187.1	239.0	352.7	471.2	580.9	517.3	356.6	210.6	127.4	108.2	89.1
97.5°	482.0	611.3	810.2	923.8	893.4	667.1	396.8	227.3	145.0	124.0	102.9
100°	961.0	1075.7	1155.0	1120.7	927.7	627.0	369.3	224.3	155.8	136.7	117.6
102.5°	1231.4	1286.3	1269.6	1130.5	864.1	568.2	345.8	228.3	168.5	151.4	134.2
105°	1390.1	1371.5	1273.6	1068.8	787.6	522.2	337.0	236.1	183.2	168.0	152.8
107.5°	1445.0	1368.6	1214.8	980.6	720.0	488.8	335.0	248.8	201.8	187.6	173.4
110°	1426.4	1302.9	1122.7	898.3	664.2	471.2	339.9	265.5	221.4	207.7	194.0

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1358.8	1216.7	1031.6	826.8	627.0	461.4	349.7	282.1	242.0	228.8	215.5
115°	1267.7	1123.7	953.2	772.0	602.5	460.4	360.5	300.8	263.5	250.3	237.1
117.5°	1175.6	1043.3	892.5	735.7	585.8	461.4	374.2	320.3	283.1	270.8	258.6
120°	1096.2	978.7	846.4	708.3	575.1	465.3	389.9	339.0	303.7	291.4	279.2
122.5°	1033.5	926.8	810.2	685.8	568.2	472.2	404.6	358.6	324.3	311.0	297.8
125°	979.7	885.6	778.8	667.1	562.3	479.1	420.3	377.2	342.9	329.6	316.4
127.5°	933.6	847.4	750.4	649.5	559.4	486.9	433.0	393.8	360.5	347.3	334.1
130°	891.5	812.1	724.0	635.8	556.4	494.7	445.7	408.5	376.2	363.0	349.7
132.5°	851.3	778.8	699.5	623.1	555.5	500.6	457.5	421.3	389.9	377.2	364.4
135°	811.2	747.5	677.9	612.3	554.5	506.5	467.3	434.0	403.6	390.4	377.2
137.5°	772.9	716.1	657.3	602.5	552.5	510.4	475.1	442.8	413.4	401.2	388.9
140°	736.7	689.7	639.7	593.7	551.5	514.3	481.0	451.6	423.2	411.0	398.7
142.5°	703.4	664.2	623.1	585.8	549.6	517.3	486.9	458.5	431.0	419.8	408.5
145°	674.0	642.7	610.3	579.0	547.6	518.2	490.8	464.4	438.9	427.6	416.4
147.5°	652.5	626.0	599.5	572.1	544.7	518.2	493.7	469.3	445.7	436.0	426.2
150°	630.9	610.3	587.8	565.3	540.8	518.2	494.7	474.2	451.6	442.8	434.0
152.5°	613.3	595.6	577.0	557.4	535.9	515.3	496.7	477.1	458.5	450.2	441.8
155°	596.6	581.9	566.2	549.6	530.0	513.3	496.7	481.0	464.4	457.5	450.6
157.5°	580.0	568.2	554.5	540.8	525.1	510.4	497.7	483.0	469.3	463.9	458.5
160°	565.3	555.5	544.7	532.0	519.2	508.4	497.7	485.9	474.2	469.3	464.4
162.5°	550.6	541.7	532.9	523.1	513.3	504.5	496.7	486.9	477.1	473.2	469.3
165°	535.9	529.0	523.1	515.3	507.5	500.6	494.7	487.9	480.0	476.6	473.2
167.5°	523.1	519.2	514.3	507.5	501.6	496.7	493.7	487.9	482.0	479.6	477.1
170°	512.4	508.4	505.5	500.6	495.7	492.8	490.8	486.9	482.0	481.0	480.0
172.5°	502.6	499.6	497.7	493.7	490.8	489.8	489.8	486.9	483.0	482.5	482.0
175°	493.7	491.8	490.8	488.8	486.9	486.9	487.9	485.9	483.9	483.4	483.0
177.5°	487.9	486.9	485.9	484.9	483.9	484.9	486.9	484.9	483.9	483.9	483.9
180°	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9	483.9

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1218.8	1218.8	1218.8	1218.8
2.5°	1187.5	1194.8	1209.5	1222.0
5°	1162.5	1174.0	1195.9	1217.8
7.5°	1132.2	1150.0	1178.2	1208.4
10°	1103.0	1126.0	1160.4	1195.9
12.5°	1073.8	1097.8	1134.3	1180.2
15°	1039.4	1064.4	1108.2	1163.5
17.5°	1009.1	1042.5	1082.1	1137.5
20°	976.7	1001.8	1052.9	1111.4
22.5°	936.1	977.8	1025.8	1087.4
25°	903.7	940.2	988.2	1058.1
27.5°	864.0	906.8	965.3	1026.8
30°	831.7	867.2	921.4	995.5
32.5°	794.1	835.9	892.2	965.3
35°	760.7	796.2	849.4	923.5
37.5°	721.1	759.7	819.2	884.9
40°	686.6	724.2	780.6	842.1
42.5°	644.9	684.6	740.9	793.1
45°	611.5	648.0	692.9	740.9
47.5°	570.8	609.4	653.3	686.6
50°	534.3	569.8	604.2	632.4
52.5°	494.6	527.0	558.3	579.2
55°	458.1	483.2	508.2	522.8
57.5°	415.3	439.3	460.2	468.5
60°	377.8	397.6	411.2	420.5
62.5°	338.1	352.7	363.2	368.4
65°	299.5	309.9	315.1	320.4
67.5°	259.8	269.2	272.4	278.6
70°	218.1	228.5	230.6	233.8
72.5°	186.8	186.8	191.0	195.1
75°	149.2	151.3	153.4	153.4
77.5°	116.9	116.9	119.0	120.0
80°	85.6	86.6	86.6	85.6
82.5°	58.4	60.5	58.4	57.4
85°	32.3	36.5	34.4	34.4
87.5°	13.6	13.6	15.7	13.6
90°	8.8	5.9	3.9	2.0
92.5°	40.2	31.3	21.6	14.7
95°	63.7	47.0	36.2	33.3
97.5°	77.4	62.7	53.9	52.9
100°	94.0	80.3	73.5	72.5
102.5°	113.6	100.9	95.0	93.1
105°	134.2	122.5	116.6	113.6
107.5°	155.8	144.0	138.1	135.2
110°	177.3	166.5	161.6	158.7

TEST NUMBER: P1012700

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	198.9	188.1	183.2	180.3
115°	220.4	210.6	204.7	200.8
117.5°	240.0	231.2	226.3	221.4
120°	260.6	250.8	245.9	243.0
122.5°	280.2	269.4	264.5	261.6
125°	297.8	287.0	281.2	279.2
127.5°	313.5	302.7	295.9	292.9
130°	329.2	317.4	308.6	305.7
132.5°	343.9	329.2	319.4	315.4
135°	356.6	341.9	331.1	327.2
137.5°	368.4	352.7	341.9	338.0
140°	379.1	363.5	353.7	348.8
142.5°	388.9	375.2	364.4	360.5
145°	399.7	385.0	376.2	373.2
147.5°	409.5	396.8	387.9	386.0
150°	420.3	407.5	399.7	398.7
152.5°	430.1	419.3	411.5	411.5
155°	439.9	430.1	424.2	424.2
157.5°	448.7	439.9	435.0	434.0
160°	457.5	449.7	445.7	445.7
162.5°	463.4	457.5	454.6	454.6
165°	469.3	464.4	462.4	463.4
167.5°	474.2	470.2	469.3	470.2
170°	478.1	475.1	474.2	476.1
172.5°	481.0	479.1	479.1	480.0
175°	483.0	481.0	482.0	483.0
177.5°	483.9	483.0	483.9	484.9
180°	483.9	483.9	483.9	483.9

(END OF REPORT)