

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012724

Luminaire Tested: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012724
REPORT IS A COMBINATION OF REPORTS P993555 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6477.0 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	90	86	89	86	83	80	72	69	67	59	57	56	47	46	45
2	89	82	76	71	81	76	71	66	63	60	57	52	50	47	42	40	39
3	82	73	66	60	75	67	61	56	56	52	48	47	43	41	38	35	33
4	75	65	57	51	68	60	53	48	50	45	42	42	38	35	34	31	29
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26
6	64	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	23	26	22	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	24	21	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12726	12726	12726	12726
5°	12736	14657	12768	10874
10°	12623	17694	12679	9498
15°	12494	20080	12494	8375
20°	12237	21660	12306	7429
25°	12050	20579	12026	6779
30°	11832	14258	11807	6143
35°	11569	9155	11517	5663
40°	11243	6464	11186	5186
45°	10674	5173	10659	4722
50°	9975	4327	9942	4179
55°	9188	3566	9116	3542
60°	8417	2948	8334	3013
65°	7513	2359	7561	2554
70°	6676	1639	6856	2065
75°	5660	1216	5892	1588
80°	4506	806	4891	1191
85°	3208	381	3496	740

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 16990 cd/sqm

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.1	1.8
10°-20°	363.5	5.6
20°-30°	572.4	8.8
30°-40°	595.2	9.2
40°-50°	509.2	7.9
50°-60°	388.3	6.0
60°-70°	248.7	3.8
70°-80°	119.2	1.8
80°-90°	33.9	0.5
90°-100°	254.7	3.9
100°-110°	745.6	11.5
110°-120°	728.1	11.2
120°-130°	579.9	9.0
130°-140°	457.5	7.1
140°-150°	341.3	5.3
150°-160°	238.0	3.7
160°-170°	139.8	2.2
170°-180°	45.5	0.7
0°-30°	1052.0	16.2
0°-40°	1647.2	25.4
0°-60°	2544.7	39.3
0°-90°	2946.6	45.5
90°-120°	1728.5	26.7
90°-150°	3107.2	48.0
90°-180°	3530.0	54.5
0°-180°	6477.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1182	1182	1182	1182	1182	
5°	1181	1404	1184	1042	1181	112
15°	1129	1995	1129	832	1129	317
25°	1026	2056	1024	677	1026	473
35°	896	892	892	552	896	561
45°	719	476	718	434	719	553
55°	507	299	503	297	507	454
65°	311	172	313	186	311	310
75°	149	73	155	95	149	161
85°	33	17	36	33	33	37
90°	2	28	2	28	2	4
95°	32	110	32	110	32	34
105°	110	1208	110	1208	110	117
115°	195	1470	195	1470	195	193
125°	271	1159	271	1159	271	241
135°	317	940	317	940	317	245
145°	362	734	362	734	362	227
155°	411	609	411	609	411	189
165°	449	531	449	531	449	127
175°	468	478	468	478	468	44
180°	469	469	469	469	469	

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3
2.5°	1185.3	1193.4	1199.5	1203.6	1213.7	1219.8	1224.8	1233.9	1233.9	1236.0	1240.0
5°	1181.3	1198.5	1210.6	1226.8	1248.1	1258.2	1272.4	1284.5	1301.7	1310.9	1320.0
7.5°	1172.2	1196.5	1221.8	1246.1	1277.5	1297.7	1311.9	1343.3	1365.5	1392.9	1414.1
10°	1160.0	1193.4	1225.8	1263.3	1305.8	1336.2	1357.4	1398.9	1441.4	1479.9	1512.3
12.5°	1144.8	1185.3	1231.9	1277.5	1337.2	1367.5	1402.0	1453.6	1514.3	1562.9	1606.4
15°	1128.7	1175.2	1227.9	1283.5	1358.4	1400.9	1450.5	1513.3	1581.1	1651.0	1710.7
17.5°	1103.3	1162.1	1220.8	1301.7	1389.8	1415.1	1457.6	1543.7	1627.7	1690.5	1763.3
20°	1078.0	1143.8	1217.7	1290.6	1385.8	1444.5	1484.0	1575.1	1665.1	1741.1	1810.9
22.5°	1054.8	1123.6	1200.5	1292.6	1381.7	1440.4	1490.0	1585.2	1689.4	1774.5	1860.5
25°	1026.4	1101.3	1186.4	1273.4	1381.7	1426.3	1480.9	1591.3	1701.6	1799.8	1906.1
27.5°	996.0	1072.0	1156.0	1245.1	1344.3	1410.1	1463.7	1582.1	1716.8	1822.0	1931.4
30°	965.7	1043.6	1124.6	1204.6	1315.9	1378.7	1440.4	1571.0	1724.9	1845.3	1929.3
32.5°	936.3	1002.1	1082.1	1160.0	1270.4	1339.2	1409.0	1559.9	1727.9	1829.1	1869.6
35°	895.8	964.7	1029.5	1112.5	1223.8	1291.6	1373.6	1558.9	1714.7	1777.5	1757.3
37.5°	858.4	916.1	977.8	1051.7	1166.1	1254.2	1339.2	1532.5	1671.2	1675.3	1560.9
40°	816.9	864.5	916.1	994.0	1117.5	1204.6	1296.7	1492.1	1592.3	1532.5	1331.1
42.5°	769.3	811.8	852.3	928.2	1062.9	1160.0	1259.2	1441.4	1477.9	1340.2	1130.7
45°	718.7	753.1	790.6	870.5	1005.2	1101.3	1200.5	1363.5	1326.0	1131.7	932.3
47.5°	666.1	695.4	731.9	804.7	943.4	1041.6	1135.7	1252.1	1157.0	948.5	781.5
50°	613.4	636.7	672.1	747.0	880.7	969.7	1056.8	1132.7	999.1	813.8	645.8
52.5°	561.8	580.0	616.5	680.2	809.8	894.8	957.6	986.9	851.3	672.1	560.8
55°	507.1	527.4	551.7	616.5	745.0	807.8	849.3	848.3	708.6	569.9	463.6
57.5°	454.5	472.7	494.0	558.8	663.0	705.5	741.0	723.8	591.2	466.6	397.8
60°	407.9	418.1	441.3	496.0	575.0	611.4	631.6	602.3	482.8	393.8	329.0
62.5°	357.3	367.4	386.7	438.3	486.9	506.1	523.3	485.9	398.8	320.9	281.4
65°	310.8	323.9	336.1	377.6	403.9	427.2	425.1	393.8	311.8	261.2	228.8
67.5°	270.3	275.3	285.5	310.8	322.9	340.1	341.1	305.7	251.0	212.6	193.3
70°	226.7	231.8	238.9	251.0	259.1	263.2	261.2	229.8	189.3	166.0	148.8
72.5°	189.3	188.3	193.3	193.3	201.4	200.4	194.4	170.1	143.7	124.5	114.4
75°	148.8	149.8	150.8	148.8	145.8	141.7	136.7	118.4	101.2	92.1	83.0
77.5°	116.4	114.4	115.4	108.3	104.3	100.2	93.1	84.0	69.8	67.8	63.8
80°	83.0	82.0	81.0	77.9	68.8	64.8	59.7	54.7	51.6	49.6	48.6
82.5°	55.7	55.7	53.6	47.6	42.5	39.5	38.5	36.4	33.4	33.4	32.4
85°	33.4	32.4	30.4	24.3	21.3	21.3	21.3	21.3	19.2	19.2	18.2
87.5°	13.2	12.1	9.1	9.1	8.1	8.1	8.1	7.1	7.1	6.1	6.1
90°	1.9	3.8	5.7	8.6	10.5	11.4	12.4	15.2	18.1	20.9	23.8
92.5°	14.3	20.9	30.4	39.0	48.5	57.0	65.6	96.0	146.3	195.7	176.7
95°	32.3	35.2	45.6	61.8	86.5	105.0	123.5	204.3	345.8	501.6	563.4
97.5°	51.3	52.3	60.8	75.1	99.8	120.2	140.6	220.4	384.8	647.0	866.5
100°	70.3	71.3	77.9	91.2	114.0	132.6	151.1	217.6	358.2	608.0	899.7
102.5°	90.3	92.2	97.9	110.2	130.2	146.8	163.4	221.4	335.4	551.0	838.0
105°	110.2	113.1	118.8	130.2	148.2	163.0	177.7	229.0	326.8	506.4	763.9
107.5°	131.1	134.0	139.7	151.1	168.2	182.0	195.7	241.3	324.9	474.1	698.3
110°	153.9	156.8	161.5	172.0	188.1	201.4	214.7	257.5	329.7	457.0	644.2

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	174.8	177.7	182.4	192.9	209.0	221.8	234.7	273.6	339.2	447.5	608.0
115°	194.8	198.6	204.3	213.8	229.9	242.8	255.6	291.7	349.6	446.5	584.3
117.5°	214.7	219.5	224.2	232.8	250.8	262.7	274.6	310.7	362.9	447.5	568.1
120°	235.6	238.5	243.2	252.7	270.8	282.6	294.5	328.7	378.1	451.3	557.7
122.5°	253.7	256.5	261.3	271.7	288.8	301.6	314.5	347.7	392.4	457.9	551.0
125°	270.8	272.7	278.4	288.8	306.9	319.7	332.5	365.8	407.6	464.6	545.3
127.5°	284.1	286.9	293.6	304.0	324.0	336.8	349.6	381.9	419.9	472.2	542.5
130°	296.4	299.3	307.8	319.2	339.2	352.0	364.8	396.2	432.3	479.8	539.6
132.5°	305.9	309.7	319.2	333.5	353.4	365.8	378.1	408.5	443.7	485.5	538.7
135°	317.3	321.1	331.6	345.8	365.8	378.6	391.4	420.9	453.2	491.2	537.7
137.5°	327.8	331.6	342.0	357.2	377.2	389.0	400.9	429.4	460.8	495.0	535.8
140°	338.2	343.0	352.5	367.7	386.7	398.5	410.4	438.0	466.5	498.8	534.9
142.5°	349.6	353.4	363.9	377.2	396.2	407.1	418.0	444.6	472.2	501.6	533.0
145°	362.0	364.8	373.4	387.6	403.8	414.7	425.6	450.3	476.0	502.6	531.1
147.5°	374.3	376.2	384.8	397.1	413.3	422.8	432.3	455.1	478.8	502.6	528.2
150°	386.7	387.6	395.2	407.6	420.9	429.4	438.0	459.8	479.8	502.6	524.4
152.5°	399.0	399.0	406.6	417.1	428.5	436.6	444.6	462.7	481.7	499.7	519.7
155°	411.4	411.4	417.1	426.6	437.0	443.6	450.3	466.5	481.7	497.8	514.0
157.5°	420.9	421.8	426.6	435.1	444.6	449.8	455.1	468.4	482.6	495.0	509.2
160°	432.3	432.3	436.1	443.7	450.3	455.0	459.8	471.2	482.6	493.1	503.5
162.5°	440.8	440.8	443.7	449.4	455.1	458.9	462.7	472.2	481.7	489.3	497.8
165°	449.4	448.4	450.3	455.1	458.9	462.2	465.5	473.1	479.8	485.5	492.1
167.5°	456.0	455.1	456.0	459.8	462.7	465.0	467.4	473.1	478.8	481.7	486.4
170°	461.7	459.8	460.8	463.6	465.5	466.4	467.4	472.2	476.0	477.9	480.7
172.5°	465.5	464.6	464.6	466.5	467.4	467.9	468.4	472.2	475.0	475.0	476.0
175°	468.4	467.4	466.5	468.4	468.4	468.8	469.3	471.2	473.1	472.2	472.2
177.5°	470.3	469.3	468.4	469.3	469.3	469.3	469.3	470.3	472.2	470.3	469.3
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3
2.5°	1248.1	1248.1	1257.2	1266.3	1261.3	1264.3	1275.4	1271.4	1279.5	1278.5	1281.5
5°	1342.2	1353.4	1362.5	1381.7	1384.8	1381.7	1400.9	1406.0	1415.1	1404.0	1409.0
7.5°	1448.5	1471.8	1494.1	1522.4	1531.5	1533.6	1543.7	1557.8	1570.0	1547.7	1558.9
10°	1551.8	1587.2	1632.8	1658.1	1680.3	1688.4	1696.5	1705.6	1719.8	1733.0	1722.8
12.5°	1663.1	1714.7	1758.3	1803.8	1831.2	1828.1	1851.4	1857.5	1868.6	1871.6	1875.7
15°	1754.2	1827.1	1854.4	1922.3	1928.3	1948.6	1974.9	1998.2	2001.2	1995.1	1995.1
17.5°	1841.3	1904.0	1952.6	2007.3	2018.4	2035.6	2069.0	2080.2	2084.2	2083.2	2083.2
20°	1912.1	1953.6	2035.6	2081.2	2099.4	2121.7	2144.9	2159.1	2162.2	2166.2	2160.1
22.5°	1958.7	2021.5	2088.3	2125.7	2140.9	2149.0	2164.2	2168.2	2163.2	2164.2	2165.2
25°	1995.1	2056.9	2097.4	2107.5	2106.5	2096.4	2085.2	2066.0	2064.0	2055.9	2039.7
27.5°	2005.3	2028.5	2023.5	1982.0	1940.5	1936.4	1869.6	1833.2	1791.7	1797.7	1774.5
30°	1950.6	1920.2	1848.4	1743.1	1699.6	1628.7	1553.8	1475.9	1445.5	1412.1	1473.8
32.5°	1817.0	1708.7	1581.1	1444.5	1371.6	1308.8	1228.9	1172.2	1139.8	1112.5	1165.1
35°	1615.5	1446.5	1277.5	1147.9	1088.2	1031.5	956.6	928.2	887.7	891.8	896.8
37.5°	1356.4	1170.2	1042.6	915.1	875.6	852.3	797.6	754.1	740.0	735.9	735.9
40°	1113.5	960.6	847.2	747.0	716.7	697.4	653.9	633.7	618.5	614.4	619.5
42.5°	921.1	790.6	702.5	635.7	614.4	590.1	571.9	546.6	543.6	536.5	545.6
45°	773.4	660.0	594.2	545.6	527.4	518.3	498.0	482.8	476.8	475.8	482.8
47.5°	655.9	567.9	510.2	479.8	465.6	456.5	439.3	433.2	427.2	429.2	426.2
50°	550.7	484.9	447.4	420.1	411.0	401.9	390.7	384.7	381.6	381.6	380.6
52.5°	472.7	418.1	393.8	368.5	364.4	359.3	347.2	343.2	338.1	337.1	341.1
55°	404.9	367.4	343.2	328.0	323.9	313.8	308.7	303.7	300.6	298.6	299.6
57.5°	346.2	317.8	301.6	288.5	281.4	277.4	268.2	267.2	265.2	265.2	264.2
60°	297.6	277.4	258.1	250.0	245.0	239.9	238.9	232.8	229.8	231.8	230.8
62.5°	252.0	235.9	224.7	215.6	212.6	208.5	205.5	203.5	200.4	201.4	201.4
65°	210.5	197.4	189.3	181.2	180.2	176.1	175.1	173.1	173.1	172.1	174.1
67.5°	173.1	164.0	156.9	151.8	148.8	149.8	145.8	142.7	142.7	141.7	144.8
70°	137.7	132.6	125.5	119.4	115.4	115.4	110.3	109.3	109.3	109.3	108.3
72.5°	106.3	97.2	94.1	92.1	92.1	92.1	90.1	90.1	89.1	90.1	89.1
75°	79.0	77.9	75.9	74.9	74.9	73.9	72.9	72.9	72.9	72.9	72.9
77.5°	61.7	61.7	59.7	58.7	58.7	58.7	57.7	57.7	56.7	56.7	56.7
80°	45.6	45.6	43.5	43.5	43.5	42.5	42.5	42.5	43.5	42.5	42.5
82.5°	31.4	31.4	30.4	31.4	30.4	29.4	29.4	29.4	28.3	29.4	29.4
85°	18.2	18.2	17.2	16.2	17.2	17.2	16.2	17.2	16.2	17.2	16.2
87.5°	7.1	6.1	6.1	6.1	5.1	6.1	5.1	5.1	6.1	5.1	6.1
90°	22.8	23.8	24.7	25.7	26.6	27.6	26.6	27.6	28.5	27.6	28.5
92.5°	132.1	94.1	73.2	63.7	60.4	57.0	55.1	51.3	52.3	50.4	52.3
95°	457.0	342.0	231.8	181.5	164.4	147.3	129.2	120.7	114.0	110.2	114.0
97.5°	895.9	785.7	592.8	467.4	413.2	359.1	295.5	259.4	236.6	226.1	236.6
100°	1086.9	1120.1	1043.2	932.0	864.6	797.1	701.2	631.8	594.7	595.7	594.7
102.5°	1096.4	1231.3	1247.4	1194.2	1157.6	1121.1	1051.7	1000.4	971.0	943.4	971.0
105°	1036.5	1235.1	1330.1	1348.2	1335.8	1323.5	1279.8	1243.6	1213.2	1208.5	1213.2
107.5°	951.0	1178.1	1327.3	1401.4	1414.2	1427.0	1421.3	1404.2	1391.9	1381.4	1391.9
110°	871.2	1088.8	1263.6	1383.3	1416.6	1449.8	1476.4	1484.0	1482.1	1480.2	1482.1

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	801.9	1000.4	1180.0	1317.8	1362.9	1408.0	1462.2	1489.7	1499.2	1500.2	1499.2
115°	748.7	924.4	1089.7	1229.4	1281.2	1333.0	1404.2	1446.0	1465.0	1469.8	1465.0
117.5°	713.5	865.5	1011.8	1140.1	1193.8	1247.4	1321.6	1368.1	1396.6	1403.3	1396.6
120°	686.9	820.9	949.1	1063.1	1111.1	1159.1	1234.1	1287.4	1310.2	1315.9	1310.2
122.5°	665.1	785.7	898.8	1002.3	1046.0	1089.7	1154.3	1200.9	1226.5	1234.1	1226.5
125°	647.0	755.3	858.9	950.1	988.1	1026.1	1086.9	1128.7	1152.4	1159.1	1152.4
127.5°	629.9	727.8	821.8	905.4	940.6	975.7	1030.8	1066.9	1088.8	1094.5	1088.8
130°	616.6	702.1	787.6	864.6	896.9	929.2	979.5	1013.7	1033.7	1041.3	1033.7
132.5°	604.2	678.4	755.3	825.6	856.0	886.4	933.0	967.2	984.3	989.0	984.3
135°	593.8	657.5	724.9	786.7	813.8	840.8	887.4	915.9	933.0	939.6	933.0
137.5°	584.3	637.5	694.5	749.6	773.8	798.1	838.0	867.4	881.7	887.4	881.7
140°	575.7	620.4	668.9	714.5	734.9	755.3	791.4	818.0	833.2	832.3	833.2
142.5°	568.1	604.2	644.2	682.2	699.3	716.4	745.8	768.6	781.9	781.0	781.9
145°	561.5	591.9	623.2	653.7	667.4	681.2	705.0	724.9	732.5	734.4	732.5
147.5°	554.8	581.4	607.1	632.8	642.8	652.7	671.7	686.0	693.6	694.5	693.6
150°	548.2	570.0	591.9	611.8	620.8	629.9	644.2	654.6	660.3	660.3	660.3
152.5°	540.6	559.6	577.6	594.7	601.8	609.0	619.4	628.9	631.8	631.8	631.8
155°	533.0	549.1	564.3	578.6	584.3	590.0	598.5	606.1	608.0	609.0	608.0
157.5°	524.4	537.7	551.0	562.4	567.2	571.9	579.5	585.2	587.1	587.1	587.1
160°	515.9	528.2	538.7	548.2	551.5	554.8	561.5	567.2	567.2	566.2	567.2
162.5°	507.3	516.8	525.4	533.9	536.8	539.6	543.4	548.2	548.2	547.2	548.2
165°	499.7	507.3	513.0	519.7	522.0	524.4	528.2	532.0	531.1	531.1	531.1
167.5°	492.1	498.8	503.5	507.3	509.2	511.1	513.0	515.9	514.9	514.9	514.9
170°	485.5	490.2	493.1	496.9	497.8	498.8	499.7	501.6	500.7	500.7	500.7
172.5°	478.8	482.6	484.5	487.4	487.8	488.3	488.3	490.2	488.3	487.4	488.3
175°	474.1	476.0	476.9	478.8	478.8	478.8	478.8	479.8	478.8	477.9	478.8
177.5°	470.3	471.2	472.2	473.1	473.1	473.1	472.2	473.1	471.2	471.2	471.2
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3
2.5°	1276.4	1270.4	1266.3	1263.3	1260.2	1269.4	1257.2	1244.1	1234.9	1228.9	1226.8
5°	1410.1	1396.9	1385.8	1376.7	1378.7	1378.7	1357.4	1334.1	1313.9	1302.8	1290.6
7.5°	1564.9	1550.8	1528.5	1523.4	1519.4	1494.1	1472.8	1430.3	1405.0	1379.7	1357.4
10°	1718.8	1700.6	1679.3	1672.2	1662.1	1630.7	1598.3	1543.7	1512.3	1465.7	1436.4
12.5°	1862.5	1840.3	1819.0	1813.9	1798.8	1771.4	1715.8	1659.1	1605.4	1555.8	1504.2
15°	1983.0	1976.9	1944.5	1924.3	1890.9	1853.4	1841.3	1764.3	1696.5	1644.9	1551.8
17.5°	2084.2	2055.9	2025.5	2012.3	1999.2	1955.7	1912.1	1833.2	1760.3	1684.4	1624.7
20°	2165.2	2133.8	2112.6	2093.3	2087.3	2037.7	1968.8	1899.0	1819.0	1734.0	1656.0
22.5°	2169.2	2165.2	2151.0	2139.9	2127.7	2095.3	2040.7	1953.6	1868.6	1775.5	1673.2
25°	2085.2	2079.2	2119.6	2109.5	2117.6	2105.5	2076.1	2003.2	1904.0	1794.7	1691.5
27.5°	1832.2	1893.9	1957.7	1980.0	1995.1	2038.7	2052.8	2012.3	1932.4	1816.0	1700.6
30°	1488.0	1570.0	1673.2	1728.9	1771.4	1852.4	1957.7	1970.8	1933.4	1840.3	1698.5
32.5°	1168.1	1243.0	1326.0	1391.8	1448.5	1614.5	1756.2	1858.5	1876.7	1828.1	1703.6
35°	941.4	973.8	1052.7	1115.5	1192.4	1334.1	1501.2	1666.2	1777.5	1783.6	1688.4
37.5°	776.4	793.6	862.4	897.9	943.4	1067.9	1223.8	1439.4	1612.5	1694.5	1645.9
40°	642.8	682.3	721.7	742.0	774.4	860.4	1010.2	1179.3	1393.9	1545.7	1580.1
42.5°	557.7	575.0	600.3	628.6	648.8	723.8	824.0	978.8	1172.2	1383.7	1478.9
45°	492.0	498.0	524.3	542.6	563.8	616.5	687.3	816.9	986.9	1195.5	1357.4
47.5°	437.3	449.4	463.6	474.7	488.9	529.4	590.1	684.3	834.1	1020.3	1194.5
50°	388.7	395.8	414.0	419.1	429.2	457.5	504.1	576.0	699.5	848.3	1028.4
52.5°	343.2	356.3	363.4	370.5	379.6	402.9	433.2	492.0	585.1	724.8	877.6
55°	307.7	311.8	321.9	328.0	335.1	351.2	377.6	421.1	494.0	605.3	750.1
57.5°	273.3	273.3	283.4	288.5	295.6	307.7	331.0	364.4	417.0	500.0	632.7
60°	236.9	237.9	246.0	252.0	254.1	266.2	285.5	311.8	352.3	413.0	521.3
62.5°	204.5	209.5	213.6	215.6	222.7	229.8	246.0	264.2	292.5	346.2	423.1
65°	177.1	178.2	181.2	183.2	186.3	194.4	206.5	218.6	242.9	282.4	345.2
67.5°	145.8	149.8	153.9	153.9	156.9	160.9	173.1	183.2	201.4	224.7	267.2
70°	109.3	111.3	117.4	120.5	124.5	131.6	137.7	143.7	157.9	175.1	207.5
72.5°	91.1	91.1	93.1	94.1	94.1	99.2	108.3	114.4	121.5	133.6	155.9
75°	72.9	72.9	75.9	74.9	76.9	79.0	80.0	84.0	88.1	97.2	110.3
77.5°	57.7	58.7	58.7	59.7	59.7	60.7	61.7	63.8	65.8	70.9	76.9
80°	42.5	43.5	43.5	44.5	44.5	45.6	46.6	47.6	49.6	51.6	54.7
82.5°	29.4	30.4	30.4	31.4	30.4	31.4	32.4	32.4	33.4	35.4	36.4
85°	17.2	17.2	18.2	17.2	17.2	17.2	18.2	18.2	19.2	22.3	22.3
87.5°	5.1	6.1	5.1	6.1	6.1	6.1	6.1	7.1	7.1	8.1	9.1
90°	27.6	26.6	27.6	26.6	25.7	24.7	23.8	22.8	23.8	20.9	18.1
92.5°	51.3	55.1	57.0	60.4	63.7	73.2	94.1	132.1	176.7	195.7	146.3
95°	120.7	129.2	147.3	164.4	181.5	231.8	342.0	457.0	563.4	501.6	345.8
97.5°	259.4	295.5	359.1	413.2	467.4	592.8	785.7	895.9	866.5	647.0	384.8
100°	631.8	701.2	797.1	864.6	932.0	1043.2	1120.1	1086.9	899.7	608.0	358.2
102.5°	1000.4	1051.7	1121.1	1157.6	1194.2	1247.4	1231.3	1096.4	838.0	551.0	335.4
105°	1243.6	1279.8	1323.5	1335.8	1348.2	1330.1	1235.1	1036.5	763.9	506.4	326.8
107.5°	1404.2	1421.3	1427.0	1414.2	1401.4	1327.3	1178.1	951.0	698.3	474.1	324.9
110°	1484.0	1476.4	1449.8	1416.6	1383.3	1263.6	1088.8	871.2	644.2	457.0	329.7

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1489.7	1462.2	1408.0	1362.9	1317.8	1180.0	1000.4	801.9	608.0	447.5	339.2
115°	1446.0	1404.2	1333.0	1281.2	1229.4	1089.7	924.4	748.7	584.3	446.5	349.6
117.5°	1368.1	1321.6	1247.4	1193.8	1140.1	1011.8	865.5	713.5	568.1	447.5	362.9
120°	1287.4	1234.1	1159.1	1111.1	1063.1	949.1	820.9	686.9	557.7	451.3	378.1
122.5°	1200.9	1154.3	1089.7	1046.0	1002.3	898.8	785.7	665.1	551.0	457.9	392.4
125°	1128.7	1086.9	1026.1	988.1	950.1	858.9	755.3	647.0	545.3	464.6	407.6
127.5°	1066.9	1030.8	975.7	940.6	905.4	821.8	727.8	629.9	542.5	472.2	419.9
130°	1013.7	979.5	929.2	896.9	864.6	787.6	702.1	616.6	539.6	479.8	432.3
132.5°	967.2	933.0	886.4	856.0	825.6	755.3	678.4	604.2	538.7	485.5	443.7
135°	915.9	887.4	840.8	813.8	786.7	724.9	657.5	593.8	537.7	491.2	453.2
137.5°	867.4	838.0	798.1	773.8	749.6	694.5	637.5	584.3	535.8	495.0	460.8
140°	818.0	791.4	755.3	734.9	714.5	668.9	620.4	575.7	534.9	498.8	466.5
142.5°	768.6	745.8	716.4	699.3	682.2	644.2	604.2	568.1	533.0	501.6	472.2
145°	724.9	705.0	681.2	667.4	653.7	623.2	591.9	561.5	531.1	502.6	476.0
147.5°	686.0	671.7	652.7	642.8	632.8	607.1	581.4	554.8	528.2	502.6	478.8
150°	654.6	644.2	629.9	620.8	611.8	591.9	570.0	548.2	524.4	502.6	479.8
152.5°	628.9	619.4	609.0	601.8	594.7	577.6	559.6	540.6	519.7	499.7	481.7
155°	606.1	598.5	590.0	584.3	578.6	564.3	549.1	533.0	514.0	497.8	481.7
157.5°	585.2	579.5	571.9	567.2	562.4	551.0	537.7	524.4	509.2	495.0	482.6
160°	567.2	561.5	554.8	551.5	548.2	538.7	528.2	515.9	503.5	493.1	482.6
162.5°	548.2	543.4	539.6	536.8	533.9	525.4	516.8	507.3	497.8	489.3	481.7
165°	532.0	528.2	524.4	522.0	519.7	513.0	507.3	499.7	492.1	485.5	479.8
167.5°	515.9	513.0	511.1	509.2	507.3	503.5	498.8	492.1	486.4	481.7	478.8
170°	501.6	499.7	498.8	497.8	496.9	493.1	490.2	485.5	480.7	477.9	476.0
172.5°	490.2	488.3	488.3	487.8	487.4	484.5	482.6	478.8	476.0	475.0	475.0
175°	479.8	478.8	478.8	478.8	478.8	476.9	476.0	474.1	472.2	472.2	473.1
177.5°	473.1	472.2	473.1	473.1	473.1	472.2	471.2	470.3	469.3	470.3	472.2
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3
2.5°	1223.8	1218.7	1213.7	1213.7	1202.5	1192.4	1187.4	1189.4	1183.3	1175.2	1167.1
5°	1277.5	1257.2	1253.2	1242.0	1226.8	1205.6	1194.5	1184.3	1172.2	1156.0	1140.8
7.5°	1327.1	1300.7	1286.6	1275.4	1246.1	1216.7	1192.4	1176.2	1155.0	1130.7	1112.5
10°	1391.8	1343.3	1328.1	1302.8	1261.3	1219.8	1191.4	1165.1	1135.7	1107.4	1083.1
12.5°	1443.5	1387.8	1359.4	1334.1	1280.5	1227.9	1180.3	1147.9	1112.5	1081.1	1049.7
15°	1502.2	1439.4	1389.8	1359.4	1291.6	1227.9	1174.2	1128.7	1089.2	1050.7	1023.4
17.5°	1530.5	1451.6	1429.3	1385.8	1287.6	1223.8	1158.0	1109.4	1061.8	1017.3	984.9
20°	1575.1	1482.9	1427.3	1397.9	1310.9	1216.7	1139.8	1084.1	1034.5	986.9	952.5
22.5°	1578.1	1477.9	1441.4	1385.8	1278.5	1195.5	1123.6	1055.8	998.1	953.5	918.1
25°	1571.0	1468.8	1418.2	1373.6	1284.5	1183.3	1091.2	1024.4	967.7	916.1	874.6
27.5°	1568.0	1442.5	1394.9	1350.3	1250.1	1147.9	1072.0	996.0	931.3	885.7	843.2
30°	1563.9	1414.1	1356.4	1304.8	1212.7	1120.6	1029.5	963.7	901.9	844.2	801.7
32.5°	1537.6	1375.6	1316.9	1262.3	1163.1	1071.0	999.1	929.2	862.4	808.8	770.3
35°	1529.5	1340.2	1263.3	1204.6	1107.4	1025.4	949.5	891.8	829.0	775.4	729.8
37.5°	1506.2	1303.8	1220.8	1145.9	1044.6	966.7	911.0	853.3	792.6	734.9	698.4
40°	1465.7	1261.3	1167.1	1090.2	985.9	907.0	855.3	812.8	753.1	701.5	656.9
42.5°	1406.0	1217.7	1116.5	1035.5	920.1	846.2	803.7	763.2	712.6	659.0	622.5
45°	1337.2	1160.0	1065.9	975.8	858.4	786.5	742.0	717.7	671.1	625.6	583.1
47.5°	1243.0	1100.3	1007.2	914.1	794.6	724.8	689.3	665.0	632.7	583.1	548.6
50°	1124.6	1023.4	935.3	852.3	731.9	665.0	629.6	611.4	584.1	548.6	515.2
52.5°	993.0	934.3	861.4	784.5	668.1	605.3	572.9	558.8	538.5	505.1	476.8
55°	860.4	835.1	785.5	709.6	601.3	549.6	521.3	503.1	487.9	463.6	439.3
57.5°	742.0	729.8	695.4	636.7	545.6	492.0	467.7	455.5	443.4	425.1	400.8
60°	619.5	632.7	597.2	567.9	484.9	438.3	417.0	403.9	397.8	381.6	366.4
62.5°	513.2	525.4	505.1	482.8	424.1	382.6	369.5	357.3	353.3	339.1	323.9
65°	417.0	432.2	417.0	404.9	369.5	335.1	318.9	312.8	308.7	299.6	287.5
67.5°	332.0	347.2	340.1	324.9	313.8	285.5	276.3	270.3	268.2	261.2	251.0
70°	250.0	271.3	273.3	264.2	254.1	240.9	234.8	232.8	227.8	221.7	215.6
72.5°	180.2	204.5	205.5	205.5	199.4	199.4	193.3	190.3	190.3	184.2	177.1
75°	132.6	148.8	150.8	152.8	155.9	158.9	154.9	154.9	153.9	147.8	144.8
77.5°	88.1	102.2	107.3	114.4	118.4	118.4	120.5	122.5	120.5	117.4	115.4
80°	56.7	66.8	72.9	76.9	83.0	86.0	89.1	90.1	88.1	87.1	84.0
82.5°	37.5	40.5	43.5	48.6	55.7	60.7	60.7	59.7	61.7	60.7	59.7
85°	21.3	23.3	24.3	25.3	29.4	34.4	35.4	36.4	38.5	36.4	34.4
87.5°	8.1	9.1	9.1	9.1	11.1	12.1	15.2	19.2	18.2	16.2	16.2
90°	15.2	12.4	11.4	10.5	8.6	5.7	3.8	1.9	3.8	5.7	8.6
92.5°	96.0	65.6	57.0	48.5	39.0	30.4	20.9	14.3	20.9	30.4	39.0
95°	204.3	123.5	105.0	86.5	61.8	45.6	35.2	32.3	35.2	45.6	61.8
97.5°	220.4	140.6	120.2	99.8	75.1	60.8	52.3	51.3	52.3	60.8	75.1
100°	217.6	151.1	132.6	114.0	91.2	77.9	71.3	70.3	71.3	77.9	91.2
102.5°	221.4	163.4	146.8	130.2	110.2	97.9	92.2	90.3	92.2	97.9	110.2
105°	229.0	177.7	163.0	148.2	130.2	118.8	113.1	110.2	113.1	118.8	130.2
107.5°	241.3	195.7	182.0	168.2	151.1	139.7	134.0	131.1	134.0	139.7	151.1
110°	257.5	214.7	201.4	188.1	172.0	161.5	156.8	153.9	156.8	161.5	172.0

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	273.6	234.7	221.8	209.0	192.9	182.4	177.7	174.8	177.7	182.4	192.9
115°	291.7	255.6	242.8	229.9	213.8	204.3	198.6	194.8	198.6	204.3	213.8
117.5°	310.7	274.6	262.7	250.8	232.8	224.2	219.5	214.7	219.5	224.2	232.8
120°	328.7	294.5	282.6	270.8	252.7	243.2	238.5	235.6	238.5	243.2	252.7
122.5°	347.7	314.5	301.6	288.8	271.7	261.3	256.5	253.7	256.5	261.3	271.7
125°	365.8	332.5	319.7	306.9	288.8	278.4	272.7	270.8	272.7	278.4	288.8
127.5°	381.9	349.6	336.8	324.0	304.0	293.6	286.9	284.1	286.9	293.6	304.0
130°	396.2	364.8	352.0	339.2	319.2	307.8	299.3	296.4	299.3	307.8	319.2
132.5°	408.5	378.1	365.8	353.4	333.5	319.2	309.7	305.9	309.7	319.2	333.5
135°	420.9	391.4	378.6	365.8	345.8	331.6	321.1	317.3	321.1	331.6	345.8
137.5°	429.4	400.9	389.0	377.2	357.2	342.0	331.6	327.8	331.6	342.0	357.2
140°	438.0	410.4	398.5	386.7	367.7	352.5	343.0	338.2	343.0	352.5	367.7
142.5°	444.6	418.0	407.1	396.2	377.2	363.9	353.4	349.6	353.4	363.9	377.2
145°	450.3	425.6	414.7	403.8	387.6	373.4	364.8	362.0	364.8	373.4	387.6
147.5°	455.1	432.3	422.8	413.3	397.1	384.8	376.2	374.3	376.2	384.8	397.1
150°	459.8	438.0	429.4	420.9	407.6	395.2	387.6	386.7	387.6	395.2	407.6
152.5°	462.7	444.6	436.6	428.5	417.1	406.6	399.0	399.0	399.0	406.6	417.1
155°	466.5	450.3	443.6	437.0	426.6	417.1	411.4	411.4	411.4	417.1	426.6
157.5°	468.4	455.1	449.8	444.6	435.1	426.6	421.8	420.9	421.8	426.6	435.1
160°	471.2	459.8	455.0	450.3	443.7	436.1	432.3	432.3	432.3	436.1	443.7
162.5°	472.2	462.7	458.9	455.1	449.4	443.7	440.8	440.8	440.8	443.7	449.4
165°	473.1	465.5	462.2	458.9	455.1	450.3	448.4	449.4	448.4	450.3	455.1
167.5°	473.1	467.4	465.0	462.7	459.8	456.0	455.1	456.0	455.1	456.0	459.8
170°	472.2	467.4	466.4	465.5	463.6	460.8	459.8	461.7	459.8	460.8	463.6
172.5°	472.2	468.4	467.9	467.4	466.5	464.6	464.6	465.5	464.6	464.6	466.5
175°	471.2	469.3	468.8	468.4	468.4	466.5	467.4	468.4	467.4	466.5	468.4
177.5°	470.3	469.3	469.3	469.3	469.3	468.4	469.3	470.3	469.3	468.4	469.3
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3
2.5°	1167.1	1162.1	1160.0	1155.0	1142.8	1134.7	1125.6	1119.5	1120.6	1115.5	1118.5
5°	1130.7	1129.7	1122.6	1112.5	1095.2	1086.1	1069.9	1061.8	1057.8	1058.8	1052.7
7.5°	1100.3	1091.2	1086.1	1069.9	1053.7	1034.5	1021.4	1014.3	1008.2	1002.1	998.1
10°	1065.9	1057.8	1049.7	1032.5	1010.2	992.0	973.8	966.7	957.6	953.5	950.5
12.5°	1029.5	1024.4	1014.3	994.0	968.7	951.5	930.3	926.2	914.1	906.0	903.9
15°	996.0	993.0	974.8	951.5	926.2	909.0	890.8	878.6	858.4	862.4	855.3
17.5°	960.6	947.5	936.3	904.9	892.8	866.5	845.2	839.2	825.0	815.9	806.8
20°	921.1	913.0	898.9	878.6	849.3	818.9	802.7	792.6	784.5	770.3	766.3
22.5°	883.7	873.6	861.4	835.1	809.8	784.5	762.2	753.1	743.0	732.9	726.8
25°	854.3	839.2	826.0	793.6	768.3	747.0	732.9	717.7	703.5	697.4	695.4
27.5°	808.8	799.7	786.5	756.1	732.9	709.6	696.4	686.3	671.1	664.0	658.0
30°	779.4	761.2	746.0	721.7	698.4	673.1	661.0	648.8	639.7	630.6	623.5
32.5°	740.0	725.8	713.6	689.3	666.1	642.8	629.6	611.4	606.3	599.2	591.2
35°	701.5	692.4	679.2	652.9	627.6	611.4	597.2	580.0	573.9	568.9	561.8
37.5°	665.0	651.9	642.8	617.5	595.2	576.0	564.8	550.7	546.6	540.5	535.5
40°	633.7	620.5	611.4	586.1	562.8	542.6	535.5	521.3	515.2	508.1	505.1
42.5°	598.2	587.1	575.0	556.7	532.4	512.2	498.0	489.9	481.8	478.8	472.7
45°	560.8	550.7	541.6	521.3	496.0	481.8	469.7	458.5	452.5	447.4	443.4
47.5°	528.4	519.3	507.1	484.9	464.6	451.5	439.3	428.2	422.1	416.0	411.0
50°	490.9	485.9	472.7	451.5	432.2	417.0	405.9	395.8	391.7	384.7	376.6
52.5°	457.5	448.4	437.3	420.1	402.9	384.7	369.5	363.4	356.3	352.3	345.2
55°	418.1	412.0	399.8	384.7	366.4	351.2	340.1	332.0	322.9	318.9	309.7
57.5°	384.7	373.5	367.4	348.2	331.0	315.8	307.7	299.6	289.5	283.4	279.4
60°	348.2	338.1	329.0	312.8	300.6	284.4	272.3	265.2	258.1	250.0	246.0
62.5°	312.8	304.7	293.6	280.4	265.2	252.0	242.9	232.8	228.8	220.7	217.6
65°	274.3	268.2	259.1	244.0	231.8	220.7	211.6	203.5	199.4	196.4	194.4
67.5°	239.9	231.8	225.7	212.6	199.4	190.3	185.2	180.2	175.1	172.1	169.0
70°	204.5	198.4	192.3	180.2	171.1	163.0	158.9	154.9	151.8	148.8	145.8
72.5°	168.0	165.0	158.9	150.8	143.7	137.7	134.6	129.6	126.5	121.5	119.4
75°	138.7	133.6	130.6	123.5	117.4	112.4	108.3	102.2	98.2	96.2	95.2
77.5°	109.3	107.3	103.2	97.2	94.1	89.1	83.0	81.0	79.0	79.0	77.9
80°	82.0	79.0	75.9	70.9	67.8	63.8	63.8	63.8	62.8	63.8	62.8
82.5°	55.7	53.6	51.6	48.6	47.6	47.6	48.6	48.6	48.6	48.6	48.6
85°	32.4	32.4	32.4	33.4	32.4	32.4	33.4	34.4	33.4	33.4	32.4
87.5°	15.2	15.2	16.2	16.2	17.2	17.2	17.2	17.2	17.2	17.2	18.2
90°	10.5	11.4	12.4	15.2	18.1	20.9	23.8	22.8	23.8	24.7	25.7
92.5°	48.5	57.0	65.6	96.0	146.3	195.7	176.7	132.1	94.1	73.2	63.7
95°	86.5	105.0	123.5	204.3	345.8	501.6	563.4	457.0	342.0	231.8	181.5
97.5°	99.8	120.2	140.6	220.4	384.8	647.0	866.5	895.9	785.7	592.8	467.4
100°	114.0	132.6	151.1	217.6	358.2	608.0	899.7	1086.9	1120.1	1043.2	932.0
102.5°	130.2	146.8	163.4	221.4	335.4	551.0	838.0	1096.4	1231.3	1247.4	1194.2
105°	148.2	163.0	177.7	229.0	326.8	506.4	763.9	1036.5	1235.1	1330.1	1348.2
107.5°	168.2	182.0	195.7	241.3	324.9	474.1	698.3	951.0	1178.1	1327.3	1401.4
110°	188.1	201.4	214.7	257.5	329.7	457.0	644.2	871.2	1088.8	1263.6	1383.3

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	209.0	221.8	234.7	273.6	339.2	447.5	608.0	801.9	1000.4	1180.0	1317.8
115°	229.9	242.8	255.6	291.7	349.6	446.5	584.3	748.7	924.4	1089.7	1229.4
117.5°	250.8	262.7	274.6	310.7	362.9	447.5	568.1	713.5	865.5	1011.8	1140.1
120°	270.8	282.6	294.5	328.7	378.1	451.3	557.7	686.9	820.9	949.1	1063.1
122.5°	288.8	301.6	314.5	347.7	392.4	457.9	551.0	665.1	785.7	898.8	1002.3
125°	306.9	319.7	332.5	365.8	407.6	464.6	545.3	647.0	755.3	858.9	950.1
127.5°	324.0	336.8	349.6	381.9	419.9	472.2	542.5	629.9	727.8	821.8	905.4
130°	339.2	352.0	364.8	396.2	432.3	479.8	539.6	616.6	702.1	787.6	864.6
132.5°	353.4	365.8	378.1	408.5	443.7	485.5	538.7	604.2	678.4	755.3	825.6
135°	365.8	378.6	391.4	420.9	453.2	491.2	537.7	593.8	657.5	724.9	786.7
137.5°	377.2	389.0	400.9	429.4	460.8	495.0	535.8	584.3	637.5	694.5	749.6
140°	386.7	398.5	410.4	438.0	466.5	498.8	534.9	575.7	620.4	668.9	714.5
142.5°	396.2	407.1	418.0	444.6	472.2	501.6	533.0	568.1	604.2	644.2	682.2
145°	403.8	414.7	425.6	450.3	476.0	502.6	531.1	561.5	591.9	623.2	653.7
147.5°	413.3	422.8	432.3	455.1	478.8	502.6	528.2	554.8	581.4	607.1	632.8
150°	420.9	429.4	438.0	459.8	479.8	502.6	524.4	548.2	570.0	591.9	611.8
152.5°	428.5	436.6	444.6	462.7	481.7	499.7	519.7	540.6	559.6	577.6	594.7
155°	437.0	443.6	450.3	466.5	481.7	497.8	514.0	533.0	549.1	564.3	578.6
157.5°	444.6	449.8	455.1	468.4	482.6	495.0	509.2	524.4	537.7	551.0	562.4
160°	450.3	455.0	459.8	471.2	482.6	493.1	503.5	515.9	528.2	538.7	548.2
162.5°	455.1	458.9	462.7	472.2	481.7	489.3	497.8	507.3	516.8	525.4	533.9
165°	458.9	462.2	465.5	473.1	479.8	485.5	492.1	499.7	507.3	513.0	519.7
167.5°	462.7	465.0	467.4	473.1	478.8	481.7	486.4	492.1	498.8	503.5	507.3
170°	465.5	466.4	467.4	472.2	476.0	477.9	480.7	485.5	490.2	493.1	496.9
172.5°	467.4	467.9	468.4	472.2	475.0	475.0	476.0	478.8	482.6	484.5	487.4
175°	468.4	468.8	469.3	471.2	473.1	472.2	472.2	474.1	476.0	476.9	478.8
177.5°	469.3	469.3	469.3	470.3	472.2	470.3	469.3	470.3	471.2	472.2	473.1
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3
2.5°	1117.5	1118.5	1115.5	1109.4	1108.4	1110.4	1116.5	1114.5	1109.4	1118.5	1110.4
5°	1055.8	1050.7	1048.7	1050.7	1044.6	1041.6	1047.7	1044.6	1047.7	1048.7	1051.7
7.5°	996.0	997.1	991.0	992.0	983.9	985.9	985.9	985.9	989.0	991.0	995.0
10°	944.4	946.4	939.4	940.4	934.3	930.3	933.3	939.4	939.4	939.4	941.4
12.5°	902.9	893.8	888.8	887.7	880.7	878.6	884.7	886.7	891.8	891.8	894.8
15°	851.3	849.3	845.2	845.2	828.0	832.1	834.1	841.2	851.3	843.2	845.2
17.5°	804.7	799.7	794.6	792.6	790.6	784.5	792.6	791.6	797.6	798.7	801.7
20°	763.2	759.2	749.1	750.1	752.1	743.0	748.0	748.0	754.1	760.2	767.3
22.5°	722.7	718.7	713.6	715.7	709.6	707.6	707.6	712.6	719.7	724.8	723.8
25°	691.4	684.3	681.2	678.2	675.2	677.2	674.2	679.2	684.3	687.3	684.3
27.5°	655.9	652.9	646.8	643.8	638.7	640.8	642.8	646.8	649.9	649.9	652.9
30°	621.5	617.5	615.4	612.4	612.4	608.4	609.4	613.4	616.5	619.5	623.5
32.5°	588.1	585.1	582.0	582.0	580.0	579.0	578.0	584.1	584.1	590.1	590.1
35°	560.8	555.7	555.7	550.7	552.7	551.7	549.6	553.7	554.7	558.8	557.7
37.5°	530.4	530.4	528.4	523.3	519.3	520.3	525.4	525.4	528.4	527.4	530.4
40°	500.0	498.0	498.0	495.0	494.0	493.0	494.0	495.0	500.0	499.0	500.0
42.5°	469.7	470.7	465.6	465.6	465.6	462.6	463.6	464.6	466.6	468.7	471.7
45°	440.3	438.3	437.3	435.3	433.2	434.3	433.2	437.3	436.3	438.3	441.3
47.5°	408.9	405.9	404.9	400.8	400.8	402.9	401.9	404.9	405.9	408.9	406.9
50°	378.6	374.5	371.5	372.5	366.4	368.5	368.5	371.5	374.5	375.5	377.6
52.5°	343.2	342.1	341.1	336.1	335.1	334.0	335.1	336.1	340.1	343.2	344.2
55°	308.7	307.7	301.6	299.6	296.6	296.6	298.6	299.6	306.7	307.7	311.8
57.5°	277.4	274.3	267.2	266.2	266.2	266.2	263.2	267.2	269.3	274.3	274.3
60°	242.9	242.9	236.9	236.9	237.9	236.9	236.9	237.9	237.9	241.9	244.0
62.5°	215.6	214.6	214.6	212.6	211.6	212.6	211.6	211.6	212.6	215.6	218.6
65°	191.3	190.3	189.3	188.3	186.3	186.3	187.3	189.3	189.3	191.3	192.3
67.5°	168.0	168.0	166.0	166.0	165.0	164.0	165.0	164.0	168.0	168.0	169.0
70°	144.8	143.7	140.7	139.7	136.7	137.7	137.7	140.7	141.7	143.7	145.8
72.5°	116.4	116.4	114.4	112.4	113.4	111.3	111.3	112.4	112.4	115.4	116.4
75°	96.2	94.1	93.1	94.1	93.1	95.2	93.1	93.1	95.2	95.2	95.2
77.5°	79.0	79.0	77.9	77.9	79.0	77.9	79.0	79.0	79.0	77.9	79.0
80°	64.8	63.8	63.8	63.8	62.8	62.8	62.8	62.8	62.8	62.8	62.8
82.5°	48.6	48.6	47.6	48.6	48.6	47.6	48.6	47.6	47.6	48.6	48.6
85°	32.4	34.4	32.4	32.4	33.4	33.4	34.4	33.4	34.4	32.4	33.4
87.5°	17.2	18.2	18.2	17.2	17.2	18.2	18.2	18.2	19.2	17.2	18.2
90°	26.6	27.6	26.6	27.6	28.5	27.6	28.5	27.6	26.6	27.6	26.6
92.5°	60.4	57.0	55.1	51.3	52.3	50.4	52.3	51.3	55.1	57.0	60.4
95°	164.4	147.3	129.2	120.7	114.0	110.2	114.0	120.7	129.2	147.3	164.4
97.5°	413.2	359.1	295.5	259.4	236.6	226.1	236.6	259.4	295.5	359.1	413.2
100°	864.6	797.1	701.2	631.8	594.7	595.7	594.7	631.8	701.2	797.1	864.6
102.5°	1157.6	1121.1	1051.7	1000.4	971.0	943.4	971.0	1000.4	1051.7	1121.1	1157.6
105°	1335.8	1323.5	1279.8	1243.6	1213.2	1208.5	1213.2	1243.6	1279.8	1323.5	1335.8
107.5°	1414.2	1427.0	1421.3	1404.2	1391.9	1381.4	1391.9	1404.2	1421.3	1427.0	1414.2
110°	1416.6	1449.8	1476.4	1484.0	1482.1	1480.2	1482.1	1484.0	1476.4	1449.8	1416.6

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1362.9	1408.0	1462.2	1489.7	1499.2	1500.2	1499.2	1489.7	1462.2	1408.0	1362.9
115°	1281.2	1333.0	1404.2	1446.0	1465.0	1469.8	1465.0	1446.0	1404.2	1333.0	1281.2
117.5°	1193.8	1247.4	1321.6	1368.1	1396.6	1403.3	1396.6	1368.1	1321.6	1247.4	1193.8
120°	1111.1	1159.1	1234.1	1287.4	1310.2	1315.9	1310.2	1287.4	1234.1	1159.1	1111.1
122.5°	1046.0	1089.7	1154.3	1200.9	1226.5	1234.1	1226.5	1200.9	1154.3	1089.7	1046.0
125°	988.1	1026.1	1086.9	1128.7	1152.4	1159.1	1152.4	1128.7	1086.9	1026.1	988.1
127.5°	940.6	975.7	1030.8	1066.9	1088.8	1094.5	1088.8	1066.9	1030.8	975.7	940.6
130°	896.9	929.2	979.5	1013.7	1033.7	1041.3	1033.7	1013.7	979.5	929.2	896.9
132.5°	856.0	886.4	933.0	967.2	984.3	989.0	984.3	967.2	933.0	886.4	856.0
135°	813.8	840.8	887.4	915.9	933.0	939.6	933.0	915.9	887.4	840.8	813.8
137.5°	773.8	798.1	838.0	867.4	881.7	887.4	881.7	867.4	838.0	798.1	773.8
140°	734.9	755.3	791.4	818.0	833.2	832.3	833.2	818.0	791.4	755.3	734.9
142.5°	699.3	716.4	745.8	768.6	781.9	781.0	781.9	768.6	745.8	716.4	699.3
145°	667.4	681.2	705.0	724.9	732.5	734.4	732.5	724.9	705.0	681.2	667.4
147.5°	642.8	652.7	671.7	686.0	693.6	694.5	693.6	686.0	671.7	652.7	642.8
150°	620.8	629.9	644.2	654.6	660.3	660.3	660.3	654.6	644.2	629.9	620.8
152.5°	601.8	609.0	619.4	628.9	631.8	631.8	631.8	628.9	619.4	609.0	601.8
155°	584.3	590.0	598.5	606.1	608.0	609.0	608.0	606.1	598.5	590.0	584.3
157.5°	567.2	571.9	579.5	585.2	587.1	587.1	587.1	585.2	579.5	571.9	567.2
160°	551.5	554.8	561.5	567.2	567.2	566.2	567.2	567.2	561.5	554.8	551.5
162.5°	536.8	539.6	543.4	548.2	548.2	547.2	548.2	548.2	543.4	539.6	536.8
165°	522.0	524.4	528.2	532.0	531.1	531.1	531.1	532.0	528.2	524.4	522.0
167.5°	509.2	511.1	513.0	515.9	514.9	514.9	514.9	515.9	513.0	511.1	509.2
170°	497.8	498.8	499.7	501.6	500.7	500.7	500.7	501.6	499.7	498.8	497.8
172.5°	487.8	488.3	488.3	490.2	488.3	487.4	488.3	490.2	488.3	488.3	487.8
175°	478.8	478.8	478.8	479.8	478.8	477.9	478.8	479.8	478.8	478.8	478.8
177.5°	473.1	473.1	472.2	473.1	471.2	471.2	471.2	473.1	472.2	473.1	473.1
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3	1182.3
2.5°	1118.5	1122.6	1118.5	1110.4	1118.5	1123.6	1128.7	1136.8	1140.8	1140.8	1146.9
5°	1054.8	1062.9	1059.8	1057.8	1065.9	1071.0	1079.1	1089.2	1100.3	1107.4	1115.5
7.5°	998.1	1003.1	1008.2	1008.2	1016.3	1027.4	1039.6	1051.7	1065.9	1076.0	1082.1
10°	948.5	952.5	955.6	959.6	971.8	983.9	1000.1	1015.3	1027.4	1038.6	1048.7
12.5°	900.9	907.0	914.1	917.1	926.2	941.4	956.6	974.8	994.0	1005.2	1015.3
15°	855.3	858.4	866.5	875.6	883.7	899.9	919.1	938.4	954.5	971.8	980.9
17.5°	808.8	809.8	831.1	826.0	852.3	867.5	877.6	895.8	922.2	936.3	950.5
20°	763.2	773.4	782.5	787.5	801.7	818.9	848.3	862.4	883.7	896.8	909.0
22.5°	727.8	743.0	743.0	755.1	762.2	778.4	799.7	827.0	850.3	859.4	876.6
25°	696.4	703.5	715.7	719.7	732.9	747.0	761.2	790.6	815.9	828.0	840.2
27.5°	655.9	665.0	681.2	681.2	698.4	713.6	730.8	750.1	775.4	792.6	805.7
30°	624.6	633.7	640.8	651.9	659.0	673.1	703.5	717.7	740.0	755.1	771.3
32.5°	595.2	602.3	608.4	620.5	628.6	644.8	661.0	686.3	705.5	719.7	736.9
35°	562.8	569.9	578.0	587.1	599.2	614.4	629.6	650.9	670.1	683.3	697.4
37.5°	532.4	537.5	549.6	555.7	565.8	580.0	599.2	621.5	638.7	648.8	663.0
40°	503.1	507.1	516.2	527.4	534.5	545.6	565.8	585.1	606.3	618.5	629.6
42.5°	471.7	476.8	484.9	496.0	507.1	519.3	530.4	552.7	571.9	582.0	594.2
45°	444.4	447.4	453.5	464.6	475.8	484.9	502.1	522.3	540.5	548.6	561.8
47.5°	412.0	415.0	424.1	429.2	441.3	453.5	470.7	490.9	507.1	515.2	527.4
50°	378.6	381.6	387.7	398.8	406.9	420.1	435.3	452.5	472.7	483.9	490.9
52.5°	346.2	352.3	357.3	366.4	376.6	389.7	403.9	420.1	437.3	448.4	456.5
55°	313.8	318.9	324.9	330.0	342.1	354.3	370.5	385.7	400.8	411.0	420.1
57.5°	277.4	284.4	290.5	300.6	309.7	319.9	338.1	350.2	368.5	375.5	383.6
60°	246.0	253.1	258.1	266.2	274.3	287.5	299.6	314.8	330.0	339.1	349.2
62.5°	219.7	222.7	225.7	233.8	241.9	254.1	266.2	281.4	297.6	302.7	310.8
65°	193.3	196.4	201.4	208.5	214.6	221.7	234.8	247.0	262.2	270.3	273.3
67.5°	171.1	174.1	175.1	180.2	185.2	193.3	200.4	212.6	226.7	231.8	237.9
70°	145.8	150.8	151.8	155.9	157.9	163.0	171.1	180.2	191.3	200.4	205.5
72.5°	116.4	123.5	125.5	131.6	134.6	139.7	145.8	152.8	159.9	164.0	168.0
75°	95.2	97.2	98.2	103.2	108.3	115.4	118.4	122.5	128.6	133.6	137.7
77.5°	79.0	80.0	81.0	81.0	82.0	86.0	92.1	97.2	101.2	103.2	106.3
80°	63.8	62.8	62.8	63.8	63.8	63.8	65.8	72.9	74.9	80.0	79.0
82.5°	49.6	47.6	48.6	47.6	47.6	47.6	47.6	48.6	48.6	51.6	53.6
85°	32.4	33.4	32.4	32.4	31.4	32.4	31.4	31.4	30.4	30.4	29.4
87.5°	17.2	18.2	17.2	17.2	16.2	17.2	16.2	16.2	15.2	15.2	13.2
90°	25.7	24.7	23.8	22.8	23.8	20.9	18.1	15.2	12.4	11.4	10.5
92.5°	63.7	73.2	94.1	132.1	176.7	195.7	146.3	96.0	65.6	57.0	48.5
95°	181.5	231.8	342.0	457.0	563.4	501.6	345.8	204.3	123.5	105.0	86.5
97.5°	467.4	592.8	785.7	895.9	866.5	647.0	384.8	220.4	140.6	120.2	99.8
100°	932.0	1043.2	1120.1	1086.9	899.7	608.0	358.2	217.6	151.1	132.6	114.0
102.5°	1194.2	1247.4	1231.3	1096.4	838.0	551.0	335.4	221.4	163.4	146.8	130.2
105°	1348.2	1330.1	1235.1	1036.5	763.9	506.4	326.8	229.0	177.7	163.0	148.2
107.5°	1401.4	1327.3	1178.1	951.0	698.3	474.1	324.9	241.3	195.7	182.0	168.2
110°	1383.3	1263.6	1088.8	871.2	644.2	457.0	329.7	257.5	214.7	201.4	188.1

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1317.8	1180.0	1000.4	801.9	608.0	447.5	339.2	273.6	234.7	221.8	209.0
115°	1229.4	1089.7	924.4	748.7	584.3	446.5	349.6	291.7	255.6	242.8	229.9
117.5°	1140.1	1011.8	865.5	713.5	568.1	447.5	362.9	310.7	274.6	262.7	250.8
120°	1063.1	949.1	820.9	686.9	557.7	451.3	378.1	328.7	294.5	282.6	270.8
122.5°	1002.3	898.8	785.7	665.1	551.0	457.9	392.4	347.7	314.5	301.6	288.8
125°	950.1	858.9	755.3	647.0	545.3	464.6	407.6	365.8	332.5	319.7	306.9
127.5°	905.4	821.8	727.8	629.9	542.5	472.2	419.9	381.9	349.6	336.8	324.0
130°	864.6	787.6	702.1	616.6	539.6	479.8	432.3	396.2	364.8	352.0	339.2
132.5°	825.6	755.3	678.4	604.2	538.7	485.5	443.7	408.5	378.1	365.8	353.4
135°	786.7	724.9	657.5	593.8	537.7	491.2	453.2	420.9	391.4	378.6	365.8
137.5°	749.6	694.5	637.5	584.3	535.8	495.0	460.8	429.4	400.9	389.0	377.2
140°	714.5	668.9	620.4	575.7	534.9	498.8	466.5	438.0	410.4	398.5	386.7
142.5°	682.2	644.2	604.2	568.1	533.0	501.6	472.2	444.6	418.0	407.1	396.2
145°	653.7	623.2	591.9	561.5	531.1	502.6	476.0	450.3	425.6	414.7	403.8
147.5°	632.8	607.1	581.4	554.8	528.2	502.6	478.8	455.1	432.3	422.8	413.3
150°	611.8	591.9	570.0	548.2	524.4	502.6	479.8	459.8	438.0	429.4	420.9
152.5°	594.7	577.6	559.6	540.6	519.7	499.7	481.7	462.7	444.6	436.6	428.5
155°	578.6	564.3	549.1	533.0	514.0	497.8	481.7	466.5	450.3	443.6	437.0
157.5°	562.4	551.0	537.7	524.4	509.2	495.0	482.6	468.4	455.1	449.8	444.6
160°	548.2	538.7	528.2	515.9	503.5	493.1	482.6	471.2	459.8	455.0	450.3
162.5°	533.9	525.4	516.8	507.3	497.8	489.3	481.7	472.2	462.7	458.9	455.1
165°	519.7	513.0	507.3	499.7	492.1	485.5	479.8	473.1	465.5	462.2	458.9
167.5°	507.3	503.5	498.8	492.1	486.4	481.7	478.8	473.1	467.4	465.0	462.7
170°	496.9	493.1	490.2	485.5	480.7	477.9	476.0	472.2	467.4	466.4	465.5
172.5°	487.4	484.5	482.6	478.8	476.0	475.0	475.0	472.2	468.4	467.9	467.4
175°	478.8	476.9	476.0	474.1	472.2	472.2	473.1	471.2	469.3	468.8	468.4
177.5°	473.1	472.2	471.2	470.3	469.3	470.3	472.2	470.3	469.3	469.3	469.3
180°	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3	469.3

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1182.3	1182.3	1182.3	1182.3
2.5°	1151.9	1159.0	1173.2	1185.3
5°	1127.6	1138.8	1160.0	1181.3
7.5°	1098.3	1115.5	1142.8	1172.2
10°	1069.9	1092.2	1125.6	1160.0
12.5°	1041.6	1064.9	1100.3	1144.8
15°	1008.2	1032.5	1075.0	1128.7
17.5°	978.8	1011.2	1049.7	1103.3
20°	947.5	971.8	1021.4	1078.0
22.5°	908.0	948.5	995.0	1054.8
25°	876.6	912.0	958.6	1026.4
27.5°	838.1	879.6	936.3	996.0
30°	806.8	841.2	893.8	965.7
32.5°	770.3	810.8	865.5	936.3
35°	737.9	772.3	824.0	895.8
37.5°	699.5	736.9	794.6	858.4
40°	666.1	702.5	757.2	816.9
42.5°	625.6	664.0	718.7	769.3
45°	593.2	628.6	672.1	718.7
47.5°	553.7	591.2	633.7	666.1
50°	518.3	552.7	586.1	613.4
52.5°	479.8	511.2	541.6	561.8
55°	444.4	468.7	493.0	507.1
57.5°	402.9	426.2	446.4	454.5
60°	366.4	385.7	398.8	407.9
62.5°	328.0	342.1	352.3	357.3
65°	290.5	300.6	305.7	310.8
67.5°	252.0	261.2	264.2	270.3
70°	211.6	221.7	223.7	226.7
72.5°	181.2	181.2	185.2	189.3
75°	144.8	146.8	148.8	148.8
77.5°	113.4	113.4	115.4	116.4
80°	83.0	84.0	84.0	83.0
82.5°	56.7	58.7	56.7	55.7
85°	31.4	35.4	33.4	33.4
87.5°	13.2	13.2	15.2	13.2
90°	8.6	5.7	3.8	1.9
92.5°	39.0	30.4	20.9	14.3
95°	61.8	45.6	35.2	32.3
97.5°	75.1	60.8	52.3	51.3
100°	91.2	77.9	71.3	70.3
102.5°	110.2	97.9	92.2	90.3
105°	130.2	118.8	113.1	110.2
107.5°	151.1	139.7	134.0	131.1
110°	172.0	161.5	156.8	153.9

TEST NUMBER: P1012724

CATALOG NUMBER: S123RDIP-B775D1025UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	192.9	182.4	177.7	174.8
115°	213.8	204.3	198.6	194.8
117.5°	232.8	224.2	219.5	214.7
120°	252.7	243.2	238.5	235.6
122.5°	271.7	261.3	256.5	253.7
125°	288.8	278.4	272.7	270.8
127.5°	304.0	293.6	286.9	284.1
130°	319.2	307.8	299.3	296.4
132.5°	333.5	319.2	309.7	305.9
135°	345.8	331.6	321.1	317.3
137.5°	357.2	342.0	331.6	327.8
140°	367.7	352.5	343.0	338.2
142.5°	377.2	363.9	353.4	349.6
145°	387.6	373.4	364.8	362.0
147.5°	397.1	384.8	376.2	374.3
150°	407.6	395.2	387.6	386.7
152.5°	417.1	406.6	399.0	399.0
155°	426.6	417.1	411.4	411.4
157.5°	435.1	426.6	421.8	420.9
160°	443.7	436.1	432.3	432.3
162.5°	449.4	443.7	440.8	440.8
165°	455.1	450.3	448.4	449.4
167.5°	459.8	456.0	455.1	456.0
170°	463.6	460.8	459.8	461.7
172.5°	466.5	464.6	464.6	465.5
175°	468.4	466.5	467.4	468.4
177.5°	469.3	468.4	469.3	470.3
180°	469.3	469.3	469.3	469.3

(END OF REPORT)