

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013060

Luminaire Tested: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013060
REPORT IS A COMBINATION OF REPORTS P996028 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6615.0 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46			39
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39			33
2	87	80	74	69	79	73	68	63	60	56	53	47	45	43	36	34	33			28
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28			24
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	25			21
5	67	55	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21			18
6	61	50	42	36	56	46	39	34	38	33	29	30	27	24	24	21	19			16
7	57	45	37	32	52	41	34	30	34	29	25	28	24	21	22	19	17			14
8	53	41	33	28	48	37	31	26	31	26	22	25	22	19	20	17	15			13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14			11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7562	7562	7562	7562
5°	7543	8675	7587	6519
10°	7487	10122	7544	5719
15°	7396	11668	7448	5117
20°	7301	12653	7353	4588
25°	7161	12508	7230	4197
30°	7025	10338	7110	3996
35°	6833	7704	6908	3875
40°	6609	5803	6673	3815
45°	6267	4658	6344	3733
50°	5859	3924	5944	3695
55°	5378	3415	5463	3652
60°	4912	3008	5057	3592
65°	4474	2588	4516	3442
70°	3960	2130	4045	3169
75°	3455	1635	3432	2692
80°	2719	1074	2686	2043
85°	1790	482	1674	1193

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 9779 cd/sqm

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.3	1.4
10°-20°	278.6	4.2
20°-30°	442.6	6.7
30°-40°	491.8	7.4
40°-50°	447.2	6.8
50°-60°	365.5	5.5
60°-70°	260.9	3.9
70°-80°	143.5	2.2
80°-90°	41.5	0.6
90°-100°	43.5	0.7
100°-110°	286.4	4.3
110°-120°	546.8	8.3
120°-130°	694.2	10.5
130°-140°	742.6	11.2
140°-150°	694.4	10.5
150°-160°	560.0	8.5
160°-170°	361.1	5.5
170°-180°	124.5	1.9
0°-30°	811.4	12.3
0°-40°	1303.2	19.7
0°-60°	2115.8	32.0
0°-90°	2561.7	38.7
90°-120°	876.6	13.3
90°-150°	3007.7	45.5
90°-180°	4053.0	61.3
0°-180°	6615.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	927	927	927	927	927	
5°	924	1088	929	818	924	88
15°	882	1494	888	655	882	249
25°	805	1587	813	532	805	371
35°	698	938	706	472	698	436
45°	557	526	564	422	557	430
55°	392	344	398	368	392	352
65°	244	221	247	294	244	241
75°	120	111	119	182	120	126
85°	25	23	23	57	25	29
90°	3	29	3	29	3	4
95°	54	28	54	28	54	66
105°	295	279	295	279	295	309
115°	551	554	551	554	551	542
125°	774	780	774	780	774	691
135°	960	967	960	967	960	740
145°	1107	1113	1107	1113	1107	692
155°	1214	1213	1214	1213	1214	560
165°	1280	1275	1280	1275	1280	362
175°	1310	1302	1310	1302	1310	125
180°	1310	1310	1310	1310	1310	

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4
2.5°	927.4	936.6	940.4	943.5	953.5	956.6	957.3	961.9	965.8	966.6	966.6
5°	923.5	938.1	949.6	960.4	976.5	983.5	991.9	1001.1	1013.4	1021.1	1024.9
7.5°	917.4	938.9	956.6	975.0	997.3	1011.1	1018.8	1043.4	1060.3	1074.1	1091.0
10°	908.2	935.8	961.2	988.1	1019.6	1036.5	1053.4	1083.3	1107.2	1134.0	1155.6
12.5°	894.3	930.4	961.2	998.8	1038.0	1058.0	1078.0	1130.2	1157.9	1181.7	1220.1
15°	882.0	918.1	961.9	1000.4	1048.8	1078.7	1107.9	1141.7	1185.5	1237.0	1273.9
17.5°	868.2	913.5	954.3	1008.0	1061.8	1090.3	1114.1	1166.3	1227.8	1278.5	1312.3
20°	849.0	895.1	948.9	1005.7	1069.5	1091.8	1123.3	1193.2	1248.5	1298.5	1353.8
22.5°	826.7	880.5	937.4	991.9	1058.0	1104.8	1139.4	1200.9	1267.7	1325.4	1387.6
25°	805.2	863.6	913.5	988.1	1058.0	1089.5	1128.7	1201.7	1274.6	1344.6	1408.3
27.5°	782.2	836.7	904.3	963.5	1042.6	1077.2	1119.4	1199.4	1277.0	1346.9	1415.3
30°	756.8	815.2	871.3	941.2	1018.0	1062.6	1101.8	1188.6	1267.7	1340.7	1404.5
32.5°	728.4	783.7	843.6	909.7	990.4	1035.7	1084.9	1174.0	1258.5	1321.5	1370.7
35°	698.4	754.5	806.7	874.4	957.3	1002.7	1050.3	1148.6	1232.4	1283.9	1312.3
37.5°	665.4	718.4	769.9	836.7	919.7	968.1	1016.5	1111.8	1190.9	1233.9	1226.2
40°	633.9	681.5	729.1	792.1	879.0	930.4	972.7	1068.7	1137.9	1156.3	1131.0
42.5°	597.8	638.5	684.6	749.1	833.6	882.0	935.0	1022.6	1074.1	1066.4	1023.4
45°	557.0	593.1	639.2	699.9	786.0	835.9	880.5	963.5	1001.1	981.9	903.5
47.5°	517.8	553.2	590.8	651.5	735.3	777.5	822.9	897.4	918.9	878.2	799.8
50°	475.6	504.8	544.0	601.6	680.0	724.5	762.2	822.1	829.8	779.8	698.4
52.5°	434.9	459.5	497.1	554.0	627.0	662.3	699.2	752.2	746.0	694.6	616.2
55°	391.8	414.9	449.5	501.7	566.3	600.1	631.6	678.4	665.4	612.4	544.0
57.5°	355.7	371.9	405.7	454.1	507.1	544.0	570.9	607.7	587.8	534.8	471.0
60°	314.2	334.2	362.6	401.8	454.1	478.7	502.5	527.1	513.2	462.5	405.7
62.5°	276.6	292.0	316.5	354.2	394.9	417.2	442.6	457.9	444.1	397.2	349.6
65°	244.3	256.6	275.8	306.6	345.7	364.2	378.8	393.4	381.9	338.1	303.5
67.5°	209.0	219.7	235.9	260.5	293.5	306.6	320.4	330.4	317.3	288.1	254.3
70°	177.5	185.2	200.5	219.0	242.0	254.3	265.8	275.8	264.3	239.7	214.4
72.5°	145.2	151.4	165.2	178.3	199.0	207.4	215.9	223.6	219.7	196.7	175.9
75°	119.9	122.2	131.4	142.1	155.2	164.4	170.6	175.2	172.1	153.7	140.6
77.5°	90.7	93.7	100.7	109.1	120.6	126.0	129.8	134.5	130.6	116.0	106.8
80°	66.1	66.8	70.7	78.4	86.1	86.8	90.7	96.8	94.5	84.5	77.6
82.5°	42.3	44.6	46.1	50.7	56.1	57.6	59.9	61.5	60.7	54.6	52.2
85°	24.6	24.6	26.1	29.2	30.7	33.0	33.8	34.6	36.1	32.3	30.0
87.5°	10.8	11.5	11.5	12.3	13.8	13.8	14.6	15.4	16.1	15.4	13.1
90°	2.9	5.3	7.7	10.1	12.5	13.7	14.6	16.3	18.1	19.8	21.6
92.5°	14.7	14.3	13.8	13.4	12.9	12.7	13.6	15.3	17.1	18.8	20.6
95°	53.9	46.5	39.1	31.7	24.3	20.6	20.7	20.9	21.2	21.4	21.6
97.5°	102.9	107.7	112.5	117.2	122.0	124.4	113.0	90.1	67.3	44.4	21.6
100°	160.7	164.6	168.5	172.4	176.3	178.3	163.3	133.2	103.2	73.1	43.1
102.5°	225.3	227.9	230.5	233.2	235.8	237.1	238.4	241.0	243.7	246.3	248.9
105°	294.9	296.2	297.5	298.8	300.1	300.8	301.3	302.4	303.5	304.6	305.7
107.5°	358.6	359.2	359.9	360.5	361.2	361.5	362.3	363.8	365.3	366.9	368.4
110°	423.2	423.9	424.5	425.2	425.9	426.2	426.9	428.2	429.5	430.8	432.1

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	485.9	487.2	488.5	489.8	491.1	491.8	492.0	492.5	492.9	493.4	493.8
115°	550.6	551.2	551.9	552.5	553.2	553.5	553.4	553.2	553.0	552.8	552.6
117.5°	608.4	609.3	610.1	611.0	611.9	612.3	612.6	613.3	614.0	614.6	615.3
120°	667.2	668.1	668.9	669.8	670.7	671.1	671.0	670.8	670.5	670.3	670.1
122.5°	722.1	722.5	722.9	723.4	723.8	724.0	724.2	724.7	725.1	725.6	726.0
125°	774.0	774.9	775.7	776.6	777.5	777.9	777.7	777.2	776.8	776.3	775.9
127.5°	824.0	824.2	824.4	824.6	824.8	824.9	825.4	826.5	827.6	828.7	829.8
130°	872.0	872.2	872.4	872.6	872.8	872.9	873.2	873.9	874.6	875.2	875.9
132.5°	916.0	916.4	916.9	917.3	917.8	918.0	918.4	919.3	920.2	921.0	921.9
135°	960.1	959.9	959.7	959.5	959.3	959.2	959.6	960.5	961.4	962.2	963.1
137.5°	999.3	999.3	999.3	999.3	999.3	999.3	999.8	1000.9	1002.0	1003.1	1004.2
140°	1037.5	1037.9	1038.4	1038.8	1039.3	1039.5	1039.7	1040.2	1040.6	1041.1	1041.5
142.5°	1071.8	1072.7	1073.5	1074.4	1075.3	1075.7	1075.8	1076.0	1076.3	1076.5	1076.7
145°	1107.1	1107.7	1108.4	1109.0	1109.7	1110.0	1110.0	1110.0	1110.0	1110.0	1110.0
147.5°	1134.5	1135.8	1137.1	1138.4	1139.7	1140.4	1140.3	1140.1	1139.8	1139.6	1139.4
150°	1164.9	1165.8	1166.6	1167.5	1168.4	1168.8	1168.7	1168.5	1168.2	1168.0	1167.8
152.5°	1190.4	1191.0	1191.7	1192.3	1193.0	1193.3	1193.1	1192.7	1192.2	1191.8	1191.4
155°	1213.9	1214.1	1214.3	1214.6	1214.8	1214.9	1214.6	1213.9	1213.2	1212.6	1211.9
157.5°	1234.5	1234.5	1234.5	1234.5	1234.5	1234.5	1234.1	1233.2	1232.3	1231.4	1230.5
160°	1252.1	1251.5	1250.8	1250.2	1249.5	1249.2	1249.1	1248.9	1248.6	1248.4	1248.2
162.5°	1267.8	1266.9	1266.1	1265.2	1264.3	1263.9	1263.8	1263.6	1263.3	1263.1	1262.9
165°	1280.5	1279.4	1278.3	1277.2	1276.1	1275.6	1275.6	1275.6	1275.6	1275.6	1275.6
167.5°	1291.3	1290.2	1289.1	1288.0	1286.9	1286.4	1286.3	1286.1	1285.8	1285.6	1285.4
170°	1300.1	1298.8	1297.5	1296.2	1294.9	1294.2	1294.3	1294.5	1294.8	1295.0	1295.2
172.5°	1306.0	1304.7	1303.4	1302.1	1300.8	1300.1	1300.2	1300.4	1300.7	1300.9	1301.1
175°	1309.9	1308.6	1307.3	1306.0	1304.7	1304.0	1304.1	1304.3	1304.6	1304.8	1305.0
177.5°	1312.8	1311.3	1309.8	1308.3	1306.8	1306.0	1306.2	1306.6	1307.1	1307.5	1307.9
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4
2.5°	968.9	982.7	988.8	990.4	998.8	993.4	995.7	995.0	1001.1	1001.9	1001.9
5°	1039.5	1055.7	1061.1	1068.7	1080.3	1083.3	1081.0	1085.6	1094.1	1087.9	1097.2
7.5°	1114.1	1131.7	1144.0	1160.9	1164.8	1174.8	1180.9	1186.3	1187.8	1188.6	1190.1
10°	1183.2	1205.5	1222.4	1250.8	1257.0	1262.4	1289.2	1278.5	1292.3	1287.7	1289.2
12.5°	1239.3	1283.1	1296.9	1344.6	1349.2	1367.6	1366.1	1383.0	1386.1	1392.2	1386.1
15°	1313.1	1363.8	1386.1	1412.9	1428.3	1449.8	1453.7	1476.7	1485.9	1494.4	1485.9
17.5°	1380.7	1407.6	1464.4	1485.9	1495.9	1507.5	1536.6	1545.1	1558.9	1553.5	1568.9
20°	1414.5	1452.9	1512.8	1549.7	1565.1	1575.8	1600.4	1613.5	1618.9	1618.9	1620.4
22.5°	1444.4	1499.8	1544.3	1586.6	1600.4	1608.1	1622.7	1632.7	1635.0	1636.5	1638.1
25°	1471.3	1521.3	1557.4	1581.2	1586.6	1586.6	1595.0	1588.9	1578.9	1586.6	1591.2
27.5°	1471.3	1506.7	1522.8	1531.3	1531.3	1510.5	1498.2	1472.9	1451.4	1445.2	1459.0
30°	1446.8	1462.9	1440.6	1419.9	1403.7	1389.9	1341.5	1303.1	1295.4	1290.0	1310.8
32.5°	1389.9	1369.2	1325.4	1265.4	1241.6	1210.1	1172.5	1143.3	1125.6	1119.4	1114.8
35°	1289.2	1235.5	1178.6	1097.9	1081.0	1041.1	989.6	968.1	938.9	938.1	948.1
37.5°	1179.4	1096.4	1034.9	958.1	934.3	892.0	843.6	821.3	801.4	786.0	804.4
40°	1051.1	978.8	885.1	822.1	788.3	766.0	725.3	700.7	691.5	683.8	695.3
42.5°	931.2	852.1	779.1	714.5	686.9	661.5	634.6	610.8	603.9	603.1	611.6
45°	812.1	734.5	666.9	611.6	593.9	578.5	552.4	545.5	534.0	526.3	530.1
47.5°	716.8	636.9	580.9	538.6	523.2	510.2	493.3	481.7	471.8	468.7	473.3
50°	623.1	569.3	511.7	476.4	464.8	452.5	439.5	428.7	424.1	421.0	424.1
52.5°	547.8	490.2	451.0	422.6	411.1	401.8	392.6	388.0	381.9	383.4	386.5
55°	480.2	429.5	396.5	375.7	368.8	365.0	353.4	348.1	345.7	344.2	345.7
57.5°	416.4	379.6	355.0	337.3	328.1	325.8	316.5	316.5	314.2	311.9	312.7
60°	365.7	334.2	310.4	296.6	295.0	291.2	285.0	284.3	278.9	281.2	282.0
62.5°	314.2	288.9	272.8	264.3	258.9	257.4	253.5	252.8	250.5	251.2	249.7
65°	273.5	252.8	236.6	229.7	227.4	226.7	223.6	221.3	219.7	221.3	219.7
67.5°	232.8	219.0	206.7	199.8	196.7	195.9	193.6	192.1	192.8	190.5	192.1
70°	194.4	180.6	172.9	169.0	167.5	165.2	165.2	165.2	165.2	163.7	162.9
72.5°	163.7	149.8	144.4	142.1	140.6	139.8	137.5	138.3	137.5	136.8	139.8
75°	129.8	121.4	116.0	113.7	115.2	112.9	110.6	112.2	109.9	110.6	113.7
77.5°	98.3	94.5	91.4	89.9	88.4	86.8	86.8	85.3	85.3	85.3	85.3
80°	71.5	70.7	65.3	64.5	64.5	63.0	63.0	63.0	63.0	62.2	63.0
82.5°	47.6	46.9	45.3	44.6	43.0	43.8	43.8	42.3	42.3	41.5	42.3
85°	27.7	27.7	26.1	25.4	24.6	25.4	23.8	23.0	23.8	23.0	23.8
87.5°	13.1	11.5	12.3	11.5	10.0	10.8	9.2	10.0	9.2	8.5	10.0
90°	22.9	24.2	25.5	26.8	27.4	27.6	28.1	28.5	29.0	29.4	29.0
92.5°	21.9	23.2	24.5	25.8	26.5	26.5	26.5	26.5	26.5	26.5	26.5
95°	22.9	24.2	25.5	26.8	27.4	27.5	27.7	28.0	28.2	28.4	28.2
97.5°	22.7	23.8	24.9	26.0	26.5	26.6	26.8	27.0	27.2	27.4	27.2
100°	39.4	35.7	32.0	28.3	26.5	26.6	26.8	27.0	27.2	27.4	27.2
102.5°	199.9	150.9	101.9	52.9	28.4	28.4	28.4	28.4	28.4	28.4	28.4
105°	307.7	309.6	311.6	313.5	314.5	310.6	302.7	294.9	287.0	279.2	287.0
107.5°	369.5	370.6	371.7	372.8	373.3	373.7	374.6	375.5	376.3	377.2	376.3
110°	432.5	432.9	433.4	433.8	434.0	434.3	435.0	435.7	436.3	437.0	436.3

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	493.6	493.4	493.1	492.9	492.8	493.2	494.1	495.0	495.8	496.7	495.8
115°	553.0	553.4	553.9	554.3	554.5	554.5	554.5	554.5	554.5	554.5	554.5
117.5°	615.1	614.9	614.6	614.4	614.3	614.3	614.3	614.3	614.3	614.3	614.3
120°	670.5	671.0	671.4	671.9	672.1	671.9	671.4	671.0	670.5	670.1	670.5
122.5°	726.2	726.4	726.7	726.9	727.0	726.8	726.3	725.9	725.4	725.0	725.4
125°	776.6	777.2	777.9	778.6	778.9	779.0	779.2	779.5	779.7	779.9	779.7
127.5°	829.6	829.4	829.2	829.0	828.9	828.8	828.6	828.3	828.1	827.9	828.1
130°	876.1	876.3	876.6	876.8	876.9	876.9	876.9	876.9	876.9	876.9	876.9
132.5°	922.1	922.3	922.6	922.8	922.9	922.8	922.6	922.3	922.1	921.9	922.1
135°	963.5	963.9	964.4	964.8	965.0	965.2	965.7	966.1	966.6	967.0	966.6
137.5°	1004.6	1005.1	1005.5	1006.0	1006.2	1006.1	1005.9	1005.6	1005.4	1005.2	1005.4
140°	1042.1	1042.8	1043.4	1044.1	1044.4	1044.5	1044.7	1045.0	1045.2	1045.4	1045.2
142.5°	1077.1	1077.6	1078.0	1078.5	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7
145°	1110.2	1110.4	1110.7	1110.9	1111.0	1111.2	1111.7	1112.1	1112.6	1113.0	1112.6
147.5°	1139.6	1139.8	1140.1	1140.3	1140.4	1140.5	1140.7	1141.0	1141.2	1141.4	1141.2
150°	1167.8	1167.8	1167.8	1167.8	1167.8	1167.9	1168.1	1168.4	1168.6	1168.8	1168.6
152.5°	1191.8	1192.2	1192.7	1193.1	1193.3	1193.2	1193.0	1192.7	1192.5	1192.3	1192.5
155°	1212.8	1213.6	1214.5	1215.4	1215.8	1215.5	1214.8	1214.2	1213.5	1212.9	1213.5
157.5°	1231.6	1232.7	1233.8	1234.9	1235.4	1234.9	1233.8	1232.7	1231.6	1230.5	1231.6
160°	1249.5	1250.8	1252.1	1253.4	1254.1	1253.4	1252.1	1250.8	1249.5	1248.2	1249.5
162.5°	1264.2	1265.5	1266.8	1268.1	1268.8	1268.0	1266.5	1265.0	1263.4	1261.9	1263.4
165°	1277.3	1279.1	1280.8	1282.5	1283.4	1282.4	1280.5	1278.5	1276.6	1274.6	1276.6
167.5°	1287.4	1289.3	1291.3	1293.2	1294.2	1293.1	1290.9	1288.8	1286.6	1284.4	1286.6
170°	1296.9	1298.7	1300.4	1302.1	1303.0	1301.9	1299.7	1297.6	1295.4	1293.2	1295.4
172.5°	1302.8	1304.6	1306.3	1308.0	1308.9	1307.7	1305.3	1302.9	1300.5	1298.1	1300.5
175°	1307.0	1308.9	1310.9	1312.8	1313.8	1312.5	1309.9	1307.3	1304.7	1302.1	1304.7
177.5°	1309.7	1311.4	1313.2	1314.9	1315.8	1314.5	1311.9	1309.2	1306.6	1304.0	1306.6
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4
2.5°	1000.4	998.1	995.0	995.0	991.1	991.1	985.0	974.2	965.0	961.9	963.5
5°	1085.6	1086.4	1081.8	1078.0	1071.0	1065.7	1055.7	1036.5	1030.3	1018.0	1009.6
7.5°	1183.2	1180.1	1171.7	1165.5	1164.0	1151.7	1130.2	1107.2	1088.7	1076.4	1058.7
10°	1293.1	1280.8	1268.5	1264.7	1255.4	1234.7	1210.1	1184.8	1159.4	1132.5	1102.5
12.5°	1385.3	1361.5	1360.7	1351.5	1333.8	1322.3	1293.1	1257.0	1213.2	1183.2	1149.4
15°	1484.4	1462.1	1443.7	1426.8	1418.3	1384.5	1359.9	1314.6	1262.4	1230.1	1207.0
17.5°	1555.1	1545.1	1513.6	1505.9	1494.4	1455.2	1416.0	1371.5	1326.1	1280.8	1218.6
20°	1611.9	1605.8	1585.1	1574.3	1555.9	1525.1	1477.5	1426.0	1373.8	1309.2	1250.8
22.5°	1636.5	1628.8	1611.9	1602.7	1591.2	1565.1	1524.4	1466.0	1397.6	1340.0	1277.7
25°	1588.1	1602.0	1597.3	1593.5	1588.9	1573.5	1542.8	1491.3	1424.5	1359.2	1281.6
27.5°	1479.0	1502.8	1525.9	1529.0	1536.6	1542.8	1530.5	1493.6	1437.5	1368.4	1283.1
30°	1332.3	1343.0	1389.9	1403.7	1414.5	1453.7	1476.7	1467.5	1424.5	1362.2	1283.9
32.5°	1144.0	1172.5	1220.1	1253.1	1282.3	1326.1	1386.1	1409.9	1394.5	1343.8	1266.2
35°	965.8	999.6	1054.9	1097.2	1126.4	1188.6	1259.3	1310.8	1330.0	1304.6	1235.5
37.5°	819.8	860.5	909.7	925.8	959.6	1036.5	1134.0	1205.5	1252.4	1254.7	1200.9
40°	709.9	730.7	769.9	794.4	827.5	892.0	987.3	1081.8	1152.5	1176.3	1147.9
42.5°	617.0	633.1	662.3	692.3	722.2	771.4	859.0	947.3	1042.6	1090.3	1089.5
45°	543.2	560.1	580.1	604.7	625.4	678.4	747.6	838.2	920.5	994.2	1012.7
47.5°	478.7	493.3	517.8	528.6	542.4	592.4	652.3	736.8	822.1	906.6	928.1
50°	431.0	443.3	460.2	467.1	482.5	519.4	568.6	636.9	731.4	809.0	849.0
52.5°	388.0	397.2	410.3	415.7	426.4	454.1	498.6	552.4	630.8	710.7	766.8
55°	351.1	357.3	366.5	372.6	380.3	404.9	437.9	486.3	554.0	623.1	677.7
57.5°	316.5	321.2	330.4	333.5	339.6	358.8	381.9	422.6	484.8	546.3	599.3
60°	284.3	287.4	292.7	299.6	304.3	317.3	338.8	372.6	422.6	478.7	521.7
62.5°	253.5	258.2	259.7	262.8	266.6	278.9	295.8	320.4	364.2	410.3	455.6
65°	222.0	225.9	229.0	229.7	233.6	242.8	258.2	279.7	308.1	348.1	390.3
67.5°	192.8	195.2	196.7	199.8	203.6	208.2	220.5	236.6	262.8	295.0	328.8
70°	166.0	166.0	168.3	169.0	173.6	179.0	184.4	199.8	222.8	248.9	272.0
72.5°	136.8	140.6	139.8	143.7	142.9	146.7	153.7	163.7	180.6	201.3	223.6
75°	111.4	113.7	113.7	113.7	115.2	118.3	122.2	131.4	144.4	161.3	174.4
77.5°	86.8	88.4	88.4	88.4	89.1	92.2	96.0	102.2	111.4	121.4	129.1
80°	62.2	63.8	63.8	65.3	65.3	66.1	69.9	73.0	77.6	85.3	93.0
82.5°	42.3	43.0	44.6	44.6	43.8	45.3	46.1	49.2	53.8	55.3	60.7
85°	23.0	23.8	24.6	24.6	25.4	26.9	26.1	29.2	29.2	32.3	33.8
87.5°	9.2	10.8	10.8	10.0	10.8	10.8	10.8	12.3	13.1	13.8	13.1
90°	28.5	28.1	27.6	27.4	26.8	25.5	24.2	22.9	21.6	19.8	18.1
92.5°	26.5	26.5	26.5	26.5	25.8	24.5	23.2	21.9	20.6	18.8	17.1
95°	28.0	27.7	27.5	27.4	26.8	25.5	24.2	22.9	21.6	21.4	21.2
97.5°	27.0	26.8	26.6	26.5	26.0	24.9	23.8	22.7	21.6	44.4	67.3
100°	27.0	26.8	26.6	26.5	28.3	32.0	35.7	39.4	43.1	73.1	103.2
102.5°	28.4	28.4	28.4	28.4	52.9	101.9	150.9	199.9	248.9	246.3	243.7
105°	294.9	302.7	310.6	314.5	313.5	311.6	309.6	307.7	305.7	304.6	303.5
107.5°	375.5	374.6	373.7	373.3	372.8	371.7	370.6	369.5	368.4	366.9	365.3
110°	435.7	435.0	434.3	434.0	433.8	433.4	432.9	432.5	432.1	430.8	429.5

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	495.0	494.1	493.2	492.8	492.9	493.1	493.4	493.6	493.8	493.4	492.9
115°	554.5	554.5	554.5	554.5	554.3	553.9	553.4	553.0	552.6	552.8	553.0
117.5°	614.3	614.3	614.3	614.3	614.4	614.6	614.9	615.1	615.3	614.6	614.0
120°	671.0	671.4	671.9	672.1	671.9	671.4	671.0	670.5	670.1	670.3	670.5
122.5°	725.9	726.3	726.8	727.0	726.9	726.7	726.4	726.2	726.0	725.6	725.1
125°	779.5	779.2	779.0	778.9	778.6	777.9	777.2	776.6	775.9	776.3	776.8
127.5°	828.3	828.6	828.8	828.9	829.0	829.2	829.4	829.6	829.8	828.7	827.6
130°	876.9	876.9	876.9	876.9	876.8	876.6	876.3	876.1	875.9	875.2	874.6
132.5°	922.3	922.6	922.8	922.9	922.8	922.6	922.3	922.1	921.9	921.0	920.2
135°	966.1	965.7	965.2	965.0	964.8	964.4	963.9	963.5	963.1	962.2	961.4
137.5°	1005.6	1005.9	1006.1	1006.2	1006.0	1005.5	1005.1	1004.6	1004.2	1003.1	1002.0
140°	1045.0	1044.7	1044.5	1044.4	1044.1	1043.4	1042.8	1042.1	1041.5	1041.1	1040.6
142.5°	1078.7	1078.7	1078.7	1078.7	1078.5	1078.0	1077.6	1077.1	1076.7	1076.5	1076.3
145°	1112.1	1111.7	1111.2	1111.0	1110.9	1110.7	1110.4	1110.2	1110.0	1110.0	1110.0
147.5°	1141.0	1140.7	1140.5	1140.4	1140.3	1140.1	1139.8	1139.6	1139.4	1139.6	1139.8
150°	1168.4	1168.1	1167.9	1167.8	1167.8	1167.8	1167.8	1167.8	1167.8	1168.0	1168.2
152.5°	1192.7	1193.0	1193.2	1193.3	1193.1	1192.7	1192.2	1191.8	1191.4	1191.8	1192.2
155°	1214.2	1214.8	1215.5	1215.8	1215.4	1214.5	1213.6	1212.8	1211.9	1212.6	1213.2
157.5°	1232.7	1233.8	1234.9	1235.4	1234.9	1233.8	1232.7	1231.6	1230.5	1231.4	1232.3
160°	1250.8	1252.1	1253.4	1254.1	1253.4	1252.1	1250.8	1249.5	1248.2	1248.4	1248.6
162.5°	1265.0	1266.5	1268.0	1268.8	1268.1	1266.8	1265.5	1264.2	1262.9	1263.1	1263.3
165°	1278.5	1280.5	1282.4	1283.4	1282.5	1280.8	1279.1	1277.3	1275.6	1275.6	1275.6
167.5°	1288.8	1290.9	1293.1	1294.2	1293.2	1291.3	1289.3	1287.4	1285.4	1285.6	1285.8
170°	1297.6	1299.7	1301.9	1303.0	1302.1	1300.4	1298.7	1296.9	1295.2	1295.0	1294.8
172.5°	1302.9	1305.3	1307.7	1308.9	1308.0	1306.3	1304.6	1302.8	1301.1	1300.9	1300.7
175°	1307.3	1309.9	1312.5	1313.8	1312.8	1310.9	1308.9	1307.0	1305.0	1304.8	1304.6
177.5°	1309.2	1311.9	1314.5	1315.8	1314.9	1313.2	1311.4	1309.7	1307.9	1307.5	1307.1
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4
2.5°	956.6	953.5	951.2	951.2	944.3	937.4	933.5	932.0	930.4	924.3	915.8
5°	995.7	985.8	978.8	971.9	960.4	948.1	935.8	928.9	918.9	905.1	895.1
7.5°	1039.5	1015.7	1008.0	999.6	976.5	955.8	938.9	924.3	908.2	890.5	872.8
10°	1076.4	1051.1	1034.2	1019.6	989.6	961.9	936.6	915.1	894.3	871.3	849.8
12.5°	1111.8	1075.7	1058.0	1036.5	1005.0	965.0	932.0	905.1	874.4	850.5	824.4
15°	1160.9	1100.2	1071.0	1057.2	1015.0	968.1	928.1	888.2	862.8	826.7	803.7
17.5°	1168.6	1119.4	1100.2	1064.9	1014.2	961.2	915.1	875.1	836.7	804.4	774.5
20°	1195.5	1131.0	1100.2	1078.0	1011.1	957.3	906.6	855.1	818.3	783.7	749.9
22.5°	1212.4	1139.4	1107.2	1071.8	1008.0	943.5	883.6	839.0	793.7	758.3	731.4
25°	1207.8	1134.8	1098.7	1065.7	988.1	923.5	869.7	812.9	770.6	732.2	696.9
27.5°	1205.5	1123.3	1084.9	1048.0	975.0	907.4	839.8	793.7	746.8	702.2	676.1
30°	1199.4	1108.7	1064.1	1024.2	948.1	877.4	819.8	766.0	719.2	678.4	643.9
32.5°	1178.6	1084.1	1041.1	998.1	918.9	848.2	789.8	739.9	693.0	650.8	617.7
35°	1150.9	1054.9	1008.0	962.7	883.6	812.1	758.3	706.1	662.3	621.6	590.1
37.5°	1123.3	1021.1	977.3	925.1	852.1	777.5	722.2	675.4	634.6	592.4	557.8
40°	1083.3	981.1	932.7	888.2	802.9	733.0	682.3	640.0	600.1	560.1	530.9
42.5°	1028.8	937.4	887.4	838.2	758.3	689.2	640.0	602.4	564.7	531.7	499.4
45°	973.5	884.3	839.8	796.0	709.2	643.9	598.5	563.9	532.4	496.3	470.2
47.5°	906.6	831.3	786.8	743.7	661.5	596.2	554.7	522.5	493.3	463.3	438.7
50°	838.2	772.9	732.2	687.6	609.3	550.1	509.4	482.5	458.7	430.3	410.3
52.5°	764.5	707.6	673.1	630.0	560.9	506.3	464.8	437.9	418.0	397.2	379.6
55°	686.1	644.6	607.7	573.2	507.9	458.7	421.8	398.0	384.2	365.0	349.6
57.5°	615.4	575.5	553.2	514.0	457.2	408.7	379.6	359.6	343.4	331.9	319.6
60°	541.7	509.4	484.8	456.4	406.4	365.7	335.0	323.5	306.6	298.1	292.7
62.5°	471.0	447.9	424.9	403.4	358.8	320.4	297.3	282.7	272.8	264.3	259.7
65°	404.1	382.6	366.5	347.3	310.4	279.7	258.2	246.6	236.6	234.3	229.0
67.5°	338.8	329.6	311.9	296.6	265.1	241.3	225.1	210.5	205.1	202.8	198.2
70°	283.5	272.8	258.9	245.9	222.0	201.3	186.7	181.3	173.6	172.9	167.5
72.5°	233.6	220.5	210.5	200.5	182.9	164.4	156.7	149.1	145.2	142.1	139.8
75°	185.2	175.9	169.0	160.6	145.2	132.9	122.2	119.1	116.8	116.0	114.5
77.5°	138.3	132.2	129.1	120.6	109.9	99.1	94.5	89.9	89.9	88.4	89.1
80°	98.3	94.5	90.7	86.1	76.8	72.2	68.4	65.3	63.8	63.0	63.8
82.5°	62.2	59.9	59.2	56.1	49.9	47.6	44.6	42.3	42.3	42.3	42.3
85°	34.6	34.6	34.6	30.0	27.7	25.4	23.8	23.0	23.0	23.0	23.8
87.5°	14.6	14.6	12.3	12.3	11.5	10.0	9.2	9.2	10.0	10.0	10.8
90°	16.3	14.6	13.7	12.5	10.1	7.7	5.3	2.9	5.3	7.7	10.1
92.5°	15.3	13.6	12.7	12.9	13.4	13.8	14.3	14.7	14.3	13.8	13.4
95°	20.9	20.7	20.6	24.3	31.7	39.1	46.5	53.9	46.5	39.1	31.7
97.5°	90.1	113.0	124.4	122.0	117.2	112.5	107.7	102.9	107.7	112.5	117.2
100°	133.2	163.3	178.3	176.3	172.4	168.5	164.6	160.7	164.6	168.5	172.4
102.5°	241.0	238.4	237.1	235.8	233.2	230.5	227.9	225.3	227.9	230.5	233.2
105°	302.4	301.3	300.8	300.1	298.8	297.5	296.2	294.9	296.2	297.5	298.8
107.5°	363.8	362.3	361.5	361.2	360.5	359.9	359.2	358.6	359.2	359.9	360.5
110°	428.2	426.9	426.2	425.9	425.2	424.5	423.9	423.2	423.9	424.5	425.2

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	492.5	492.0	491.8	491.1	489.8	488.5	487.2	485.9	487.2	488.5	489.8
115°	553.2	553.4	553.5	553.2	552.5	551.9	551.2	550.6	551.2	551.9	552.5
117.5°	613.3	612.6	612.3	611.9	611.0	610.1	609.3	608.4	609.3	610.1	611.0
120°	670.8	671.0	671.1	670.7	669.8	668.9	668.1	667.2	668.1	668.9	669.8
122.5°	724.7	724.2	724.0	723.8	723.4	722.9	722.5	722.1	722.5	722.9	723.4
125°	777.2	777.7	777.9	777.5	776.6	775.7	774.9	774.0	774.9	775.7	776.6
127.5°	826.5	825.4	824.9	824.8	824.6	824.4	824.2	824.0	824.2	824.4	824.6
130°	873.9	873.2	872.9	872.8	872.6	872.4	872.2	872.0	872.2	872.4	872.6
132.5°	919.3	918.4	918.0	917.8	917.3	916.9	916.4	916.0	916.4	916.9	917.3
135°	960.5	959.6	959.2	959.3	959.5	959.7	959.9	960.1	959.9	959.7	959.5
137.5°	1000.9	999.8	999.3	999.3	999.3	999.3	999.3	999.3	999.3	999.3	999.3
140°	1040.2	1039.7	1039.5	1039.3	1038.8	1038.4	1037.9	1037.5	1037.9	1038.4	1038.8
142.5°	1076.0	1075.8	1075.7	1075.3	1074.4	1073.5	1072.7	1071.8	1072.7	1073.5	1074.4
145°	1110.0	1110.0	1110.0	1109.7	1109.0	1108.4	1107.7	1107.1	1107.7	1108.4	1109.0
147.5°	1140.1	1140.3	1140.4	1139.7	1138.4	1137.1	1135.8	1134.5	1135.8	1137.1	1138.4
150°	1168.5	1168.7	1168.8	1168.4	1167.5	1166.6	1165.8	1164.9	1165.8	1166.6	1167.5
152.5°	1192.7	1193.1	1193.3	1193.0	1192.3	1191.7	1191.0	1190.4	1191.0	1191.7	1192.3
155°	1213.9	1214.6	1214.9	1214.8	1214.6	1214.3	1214.1	1213.9	1214.1	1214.3	1214.6
157.5°	1233.2	1234.1	1234.5	1234.5	1234.5	1234.5	1234.5	1234.5	1234.5	1234.5	1234.5
160°	1248.9	1249.1	1249.2	1249.5	1250.2	1250.8	1251.5	1252.1	1251.5	1250.8	1250.2
162.5°	1263.6	1263.8	1263.9	1264.3	1265.2	1266.1	1266.9	1267.8	1266.9	1266.1	1265.2
165°	1275.6	1275.6	1275.6	1276.1	1277.2	1278.3	1279.4	1280.5	1279.4	1278.3	1277.2
167.5°	1286.1	1286.3	1286.4	1286.9	1288.0	1289.1	1290.2	1291.3	1290.2	1289.1	1288.0
170°	1294.5	1294.3	1294.2	1294.9	1296.2	1297.5	1298.8	1300.1	1298.8	1297.5	1296.2
172.5°	1300.4	1300.2	1300.1	1300.8	1302.1	1303.4	1304.7	1306.0	1304.7	1303.4	1302.1
175°	1304.3	1304.1	1304.0	1304.7	1306.0	1307.3	1308.6	1309.9	1308.6	1307.3	1306.0
177.5°	1306.6	1306.2	1306.0	1306.8	1308.3	1309.8	1311.3	1312.8	1311.3	1309.8	1308.3
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4
2.5°	913.5	910.5	912.0	904.3	897.4	887.4	879.0	877.4	875.9	880.5	877.4
5°	887.4	883.6	879.7	870.5	856.7	848.2	835.9	835.2	830.6	823.6	825.2
7.5°	859.0	856.7	851.3	836.7	824.4	809.8	799.8	791.4	787.5	781.4	779.1
10°	835.9	827.5	822.9	806.7	792.1	776.8	763.7	757.6	750.7	745.3	741.4
12.5°	804.4	802.1	789.1	776.0	763.7	746.0	736.1	718.4	709.2	713.8	712.2
15°	783.7	772.9	769.9	751.4	730.7	719.2	700.7	689.2	685.3	678.4	670.0
17.5°	756.0	749.1	738.4	721.5	697.6	681.5	668.4	657.7	653.1	643.9	636.9
20°	729.9	718.4	709.9	694.6	671.5	650.8	634.6	627.7	616.2	608.5	604.7
22.5°	706.1	697.6	685.3	662.3	642.3	622.3	603.1	593.1	582.4	577.8	571.6
25°	676.9	663.1	654.6	629.3	607.7	591.6	573.9	560.9	554.7	547.0	545.5
27.5°	648.5	635.4	625.4	603.1	577.0	556.3	545.5	536.3	525.5	525.5	521.7
30°	620.0	610.8	595.5	573.9	549.4	529.4	517.1	508.6	504.8	501.7	500.9
32.5°	591.6	579.3	570.1	540.9	522.5	504.0	494.8	487.9	483.3	482.5	483.3
35°	562.4	548.6	539.4	513.2	494.8	477.9	474.1	467.9	465.6	464.8	468.7
37.5°	531.7	520.9	509.4	487.9	467.1	457.2	449.5	447.2	446.4	451.0	452.5
40°	503.3	494.0	483.3	460.2	444.9	434.1	430.3	428.0	431.0	435.6	437.9
42.5°	476.4	463.3	454.8	434.1	420.3	414.1	409.5	409.5	412.6	418.0	421.8
45°	447.9	437.9	429.5	411.1	398.8	391.8	391.1	391.8	395.7	399.5	404.1
47.5°	420.3	410.3	401.1	385.7	374.9	371.1	370.3	371.1	377.2	382.6	388.0
50°	394.9	384.2	375.7	361.1	352.7	348.1	348.8	352.7	357.3	365.0	371.9
52.5°	365.0	357.3	349.6	336.5	328.8	325.8	328.1	331.1	339.6	345.0	353.4
55°	335.8	328.8	322.7	312.7	306.6	304.3	305.8	310.4	317.3	326.5	336.5
57.5°	308.9	301.2	295.0	288.1	281.2	282.0	282.7	288.9	297.3	305.8	317.3
60°	278.9	274.3	268.9	260.5	257.4	257.4	259.7	266.6	274.3	288.1	298.1
62.5°	252.0	245.9	242.0	236.6	232.0	232.8	238.2	244.3	253.5	265.1	278.1
65°	224.4	217.4	214.4	209.8	208.2	209.0	212.8	222.0	232.0	242.0	254.3
67.5°	193.6	191.3	188.2	183.6	185.2	185.9	189.8	197.5	208.2	218.2	232.0
70°	167.5	162.9	162.1	158.3	158.3	160.6	168.3	173.6	183.6	194.4	209.0
72.5°	139.8	136.0	136.0	132.9	135.2	137.5	141.4	149.1	158.3	169.0	181.3
75°	111.4	109.9	111.4	109.9	109.9	113.7	118.3	124.5	134.5	146.0	156.0
77.5°	86.1	86.1	85.3	87.6	87.6	89.9	96.0	102.2	109.9	119.1	129.8
80°	63.0	63.0	63.0	65.3	67.6	67.6	71.5	79.1	86.1	92.2	102.2
82.5°	43.0	43.0	43.0	44.6	47.6	47.6	52.2	56.9	64.5	69.9	74.5
85°	26.1	26.1	25.4	26.9	27.7	30.0	33.8	36.9	40.7	45.3	49.9
87.5°	11.5	11.5	12.3	13.1	13.8	15.4	16.9	18.4	22.3	23.8	26.1
90°	12.5	13.7	14.6	16.3	18.1	19.8	21.6	22.9	24.2	25.5	26.8
92.5°	12.9	12.7	13.6	15.3	17.1	18.8	20.6	21.9	23.2	24.5	25.8
95°	24.3	20.6	20.7	20.9	21.2	21.4	21.6	22.9	24.2	25.5	26.8
97.5°	122.0	124.4	113.0	90.1	67.3	44.4	21.6	22.7	23.8	24.9	26.0
100°	176.3	178.3	163.3	133.2	103.2	73.1	43.1	39.4	35.7	32.0	28.3
102.5°	235.8	237.1	238.4	241.0	243.7	246.3	248.9	199.9	150.9	101.9	52.9
105°	300.1	300.8	301.3	302.4	303.5	304.6	305.7	307.7	309.6	311.6	313.5
107.5°	361.2	361.5	362.3	363.8	365.3	366.9	368.4	369.5	370.6	371.7	372.8
110°	425.9	426.2	426.9	428.2	429.5	430.8	432.1	432.5	432.9	433.4	433.8

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	491.1	491.8	492.0	492.5	492.9	493.4	493.8	493.6	493.4	493.1	492.9
115°	553.2	553.5	553.4	553.2	553.0	552.8	552.6	553.0	553.4	553.9	554.3
117.5°	611.9	612.3	612.6	613.3	614.0	614.6	615.3	615.1	614.9	614.6	614.4
120°	670.7	671.1	671.0	670.8	670.5	670.3	670.1	670.5	671.0	671.4	671.9
122.5°	723.8	724.0	724.2	724.7	725.1	725.6	726.0	726.2	726.4	726.7	726.9
125°	777.5	777.9	777.7	777.2	776.8	776.3	775.9	776.6	777.2	777.9	778.6
127.5°	824.8	824.9	825.4	826.5	827.6	828.7	829.8	829.6	829.4	829.2	829.0
130°	872.8	872.9	873.2	873.9	874.6	875.2	875.9	876.1	876.3	876.6	876.8
132.5°	917.8	918.0	918.4	919.3	920.2	921.0	921.9	922.1	922.3	922.6	922.8
135°	959.3	959.2	959.6	960.5	961.4	962.2	963.1	963.5	963.9	964.4	964.8
137.5°	999.3	999.3	999.8	1000.9	1002.0	1003.1	1004.2	1004.6	1005.1	1005.5	1006.0
140°	1039.3	1039.5	1039.7	1040.2	1040.6	1041.1	1041.5	1042.1	1042.8	1043.4	1044.1
142.5°	1075.3	1075.7	1075.8	1076.0	1076.3	1076.5	1076.7	1077.1	1077.6	1078.0	1078.5
145°	1109.7	1110.0	1110.0	1110.0	1110.0	1110.0	1110.0	1110.2	1110.4	1110.7	1110.9
147.5°	1139.7	1140.4	1140.3	1140.1	1139.8	1139.6	1139.4	1139.6	1139.8	1140.1	1140.3
150°	1168.4	1168.8	1168.7	1168.5	1168.2	1168.0	1167.8	1167.8	1167.8	1167.8	1167.8
152.5°	1193.0	1193.3	1193.1	1192.7	1192.2	1191.8	1191.4	1191.8	1192.2	1192.7	1193.1
155°	1214.8	1214.9	1214.6	1213.9	1213.2	1212.6	1211.9	1212.8	1213.6	1214.5	1215.4
157.5°	1234.5	1234.5	1234.1	1233.2	1232.3	1231.4	1230.5	1231.6	1232.7	1233.8	1234.9
160°	1249.5	1249.2	1249.1	1248.9	1248.6	1248.4	1248.2	1249.5	1250.8	1252.1	1253.4
162.5°	1264.3	1263.9	1263.8	1263.6	1263.3	1263.1	1262.9	1264.2	1265.5	1266.8	1268.1
165°	1276.1	1275.6	1275.6	1275.6	1275.6	1275.6	1275.6	1277.3	1279.1	1280.8	1282.5
167.5°	1286.9	1286.4	1286.3	1286.1	1285.8	1285.6	1285.4	1287.4	1289.3	1291.3	1293.2
170°	1294.9	1294.2	1294.3	1294.5	1294.8	1295.0	1295.2	1296.9	1298.7	1300.4	1302.1
172.5°	1300.8	1300.1	1300.2	1300.4	1300.7	1300.9	1301.1	1302.8	1304.6	1306.3	1308.0
175°	1304.7	1304.0	1304.1	1304.3	1304.6	1304.8	1305.0	1307.0	1308.9	1310.9	1312.8
177.5°	1306.8	1306.0	1306.2	1306.6	1307.1	1307.5	1307.9	1309.7	1311.4	1313.2	1314.9
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4
2.5°	875.1	874.4	870.5	872.0	867.4	869.0	871.3	872.0	875.1	872.8	872.0
5°	821.3	819.8	817.5	815.2	814.4	817.5	812.1	813.7	815.2	817.5	820.6
7.5°	777.5	776.8	774.5	770.6	769.1	767.6	768.3	773.7	772.9	772.2	777.5
10°	737.6	738.4	733.7	733.0	728.4	727.6	728.4	729.9	732.2	735.3	736.1
12.5°	696.1	706.1	697.6	694.6	687.6	691.5	693.0	686.1	690.0	692.3	703.8
15°	670.0	665.4	660.0	660.0	656.9	655.4	651.5	656.9	660.0	664.6	663.1
17.5°	633.9	626.2	623.1	620.0	620.8	623.9	615.4	627.7	627.7	630.0	626.2
20°	602.4	596.2	592.4	590.8	588.5	587.0	586.2	589.3	593.9	595.5	599.3
22.5°	569.3	569.3	563.2	560.9	559.3	557.0	560.9	558.6	561.6	564.7	570.9
25°	541.7	541.7	539.4	536.3	534.0	532.4	534.8	534.0	536.3	540.1	541.7
27.5°	519.4	517.1	516.3	515.5	514.8	515.5	514.8	517.1	519.4	520.2	518.6
30°	500.2	497.9	498.6	498.6	499.4	498.6	497.9	500.2	500.9	499.4	500.2
32.5°	482.5	482.5	484.0	484.8	484.8	485.6	486.3	484.8	485.6	483.3	484.0
35°	467.9	469.4	471.0	471.8	472.5	471.8	473.3	472.5	471.0	469.4	468.7
37.5°	453.3	454.8	457.9	458.7	461.0	461.8	460.2	460.2	459.5	456.4	454.8
40°	437.9	439.5	443.3	445.6	447.2	449.5	447.9	447.9	444.9	441.8	439.5
42.5°	423.3	426.4	430.3	432.6	435.6	435.6	435.6	434.1	430.3	427.2	424.9
45°	408.7	409.5	414.9	418.7	421.8	421.8	421.8	419.5	417.2	411.1	408.0
47.5°	392.6	394.9	401.1	404.9	408.0	408.7	408.7	406.4	401.8	396.5	392.6
50°	374.9	378.8	385.7	391.1	394.9	396.5	394.1	392.6	387.2	381.1	376.5
52.5°	358.0	362.6	371.1	375.7	381.1	381.9	381.1	378.8	372.6	364.2	360.3
55°	341.1	345.0	354.2	361.9	366.5	368.0	366.5	362.6	355.0	346.5	342.7
57.5°	322.7	328.1	338.1	345.7	351.1	351.9	350.4	346.5	340.4	329.6	324.2
60°	303.5	310.4	320.4	328.1	335.0	335.8	334.2	328.8	321.2	310.4	305.8
62.5°	284.3	289.7	301.2	309.6	315.0	318.9	315.8	310.4	302.7	292.0	285.0
65°	262.0	269.7	279.7	287.4	293.5	294.3	292.7	288.1	279.7	268.1	262.8
67.5°	240.5	245.9	255.9	265.8	268.1	270.4	268.1	263.5	256.6	246.6	238.9
70°	214.4	219.0	231.3	238.2	241.3	243.6	242.0	237.4	231.3	222.0	215.9
72.5°	188.2	192.1	203.6	209.0	215.1	214.4	213.6	210.5	202.1	195.9	192.1
75°	160.6	165.2	172.9	179.8	182.1	182.1	182.1	179.8	174.4	164.4	160.6
77.5°	135.2	137.5	143.7	147.5	149.8	150.6	149.8	146.0	142.9	136.0	133.7
80°	103.7	109.9	114.5	115.2	118.3	118.3	118.3	116.8	113.7	106.8	106.0
82.5°	78.4	79.9	84.5	86.8	88.4	87.6	87.6	84.5	83.7	79.9	78.4
85°	53.0	55.3	54.6	57.6	58.4	56.9	56.9	58.4	54.6	55.3	53.0
87.5°	29.2	29.2	30.7	30.0	33.0	33.0	31.5	32.3	30.7	30.0	29.2
90°	27.4	27.6	28.1	28.5	29.0	29.4	29.0	28.5	28.1	27.6	27.4
92.5°	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5
95°	27.4	27.5	27.7	28.0	28.2	28.4	28.2	28.0	27.7	27.5	27.4
97.5°	26.5	26.6	26.8	27.0	27.2	27.4	27.2	27.0	26.8	26.6	26.5
100°	26.5	26.6	26.8	27.0	27.2	27.4	27.2	27.0	26.8	26.6	26.5
102.5°	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4
105°	314.5	310.6	302.7	294.9	287.0	279.2	287.0	294.9	302.7	310.6	314.5
107.5°	373.3	373.7	374.6	375.5	376.3	377.2	376.3	375.5	374.6	373.7	373.3
110°	434.0	434.3	435.0	435.7	436.3	437.0	436.3	435.7	435.0	434.3	434.0

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	492.8	493.2	494.1	495.0	495.8	496.7	495.8	495.0	494.1	493.2	492.8
115°	554.5	554.5	554.5	554.5	554.5	554.5	554.5	554.5	554.5	554.5	554.5
117.5°	614.3	614.3	614.3	614.3	614.3	614.3	614.3	614.3	614.3	614.3	614.3
120°	672.1	671.9	671.4	671.0	670.5	670.1	670.5	671.0	671.4	671.9	672.1
122.5°	727.0	726.8	726.3	725.9	725.4	725.0	725.4	725.9	726.3	726.8	727.0
125°	778.9	779.0	779.2	779.5	779.7	779.9	779.7	779.5	779.2	779.0	778.9
127.5°	828.9	828.8	828.6	828.3	828.1	827.9	828.1	828.3	828.6	828.8	828.9
130°	876.9	876.9	876.9	876.9	876.9	876.9	876.9	876.9	876.9	876.9	876.9
132.5°	922.9	922.8	922.6	922.3	922.1	921.9	922.1	922.3	922.6	922.8	922.9
135°	965.0	965.2	965.7	966.1	966.6	967.0	966.6	966.1	965.7	965.2	965.0
137.5°	1006.2	1006.1	1005.9	1005.6	1005.4	1005.2	1005.4	1005.6	1005.9	1006.1	1006.2
140°	1044.4	1044.5	1044.7	1045.0	1045.2	1045.4	1045.2	1045.0	1044.7	1044.5	1044.4
142.5°	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7	1078.7
145°	1111.0	1111.2	1111.7	1112.1	1112.6	1113.0	1112.6	1112.1	1111.7	1111.2	1111.0
147.5°	1140.4	1140.5	1140.7	1141.0	1141.2	1141.4	1141.2	1141.0	1140.7	1140.5	1140.4
150°	1167.8	1167.9	1168.1	1168.4	1168.6	1168.8	1168.6	1168.4	1168.1	1167.9	1167.8
152.5°	1193.3	1193.2	1193.0	1192.7	1192.5	1192.3	1192.5	1192.7	1193.0	1193.2	1193.3
155°	1215.8	1215.5	1214.8	1214.2	1213.5	1212.9	1213.5	1214.2	1214.8	1215.5	1215.8
157.5°	1235.4	1234.9	1233.8	1232.7	1231.6	1230.5	1231.6	1232.7	1233.8	1234.9	1235.4
160°	1254.1	1253.4	1252.1	1250.8	1249.5	1248.2	1249.5	1250.8	1252.1	1253.4	1254.1
162.5°	1268.8	1268.0	1266.5	1265.0	1263.4	1261.9	1263.4	1265.0	1266.5	1268.0	1268.8
165°	1283.4	1282.4	1280.5	1278.5	1276.6	1274.6	1276.6	1278.5	1280.5	1282.4	1283.4
167.5°	1294.2	1293.1	1290.9	1288.8	1286.6	1284.4	1286.6	1288.8	1290.9	1293.1	1294.2
170°	1303.0	1301.9	1299.7	1297.6	1295.4	1293.2	1295.4	1297.6	1299.7	1301.9	1303.0
172.5°	1308.9	1307.7	1305.3	1302.9	1300.5	1298.1	1300.5	1302.9	1305.3	1307.7	1308.9
175°	1313.8	1312.5	1309.9	1307.3	1304.7	1302.1	1304.7	1307.3	1309.9	1312.5	1313.8
177.5°	1315.8	1314.5	1311.9	1309.2	1306.6	1304.0	1306.6	1309.2	1311.9	1314.5	1315.8
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4	927.4
2.5°	872.0	876.7	872.0	875.1	876.7	880.5	882.0	888.9	891.3	896.6	896.6
5°	819.8	822.1	822.9	825.9	829.0	836.7	842.1	852.1	863.6	865.1	872.0
7.5°	777.5	781.4	787.5	785.2	790.6	802.1	809.0	821.3	832.9	839.0	847.5
10°	739.9	744.5	746.8	749.1	759.1	769.1	779.8	788.3	803.7	812.9	819.8
12.5°	709.2	705.3	709.9	718.4	729.9	736.1	750.7	763.7	775.2	785.2	791.4
15°	669.2	672.3	676.9	691.5	694.6	709.9	715.3	729.9	751.4	760.6	768.3
17.5°	630.8	640.8	650.0	655.4	664.6	676.9	692.3	708.4	722.2	733.0	742.2
20°	600.1	610.0	615.4	619.3	628.5	645.4	660.0	680.0	697.6	706.1	718.4
22.5°	575.5	575.5	583.2	594.7	600.1	616.2	628.5	650.0	669.2	680.0	691.5
25°	544.7	549.4	555.5	565.5	573.2	586.2	603.9	622.3	643.1	652.3	666.9
27.5°	519.4	524.8	533.2	535.5	543.2	554.7	573.2	593.1	614.7	624.6	636.9
30°	500.2	503.3	506.3	510.9	517.8	527.8	543.2	560.9	587.0	594.7	610.0
32.5°	483.3	484.8	486.3	490.2	494.0	504.0	516.3	535.5	557.0	568.6	582.4
35°	467.9	466.4	467.1	469.4	473.3	477.1	490.2	506.3	526.3	540.1	550.9
37.5°	453.3	450.2	449.5	449.5	451.0	455.6	465.6	479.4	500.9	512.5	523.2
40°	437.2	434.1	432.6	431.8	431.0	434.1	441.8	455.6	472.5	483.3	495.6
42.5°	421.8	418.7	414.9	414.1	412.6	414.1	419.5	432.6	447.2	457.9	467.9
45°	406.4	401.1	396.5	393.4	394.1	391.8	395.7	405.7	422.6	429.5	439.5
47.5°	389.5	383.4	377.2	374.2	371.1	372.6	374.2	382.6	397.2	404.1	414.1
50°	373.4	365.0	358.0	354.2	351.9	350.4	351.9	360.3	371.1	377.2	385.7
52.5°	355.0	346.5	339.6	333.5	330.4	328.1	328.8	336.5	346.5	352.7	361.1
55°	338.1	327.3	318.1	310.4	308.1	307.3	306.6	311.9	320.4	326.5	333.5
57.5°	318.9	308.1	298.1	288.9	284.3	283.5	283.5	285.0	295.8	300.4	304.3
60°	299.6	288.1	277.4	268.9	262.0	259.7	258.9	262.0	267.4	272.0	277.4
62.5°	278.1	266.6	253.5	245.9	238.9	232.8	235.1	235.9	243.6	245.9	250.5
65°	257.4	244.3	233.6	221.3	213.6	209.8	208.2	209.8	215.9	216.7	219.7
67.5°	233.6	221.3	208.2	199.8	192.8	185.9	184.4	184.4	187.5	189.8	193.6
70°	210.5	198.2	183.6	174.4	167.5	161.3	159.0	158.3	160.6	162.1	166.0
72.5°	183.6	171.3	160.6	150.6	142.1	137.5	135.2	133.7	136.0	137.5	138.3
75°	155.2	145.2	134.5	124.5	119.1	114.5	111.4	109.1	110.6	110.6	110.6
77.5°	128.3	118.3	109.9	103.0	96.0	90.7	88.4	86.1	86.8	86.8	88.4
80°	99.9	93.0	86.1	79.9	73.8	69.1	67.6	65.3	63.8	63.0	63.0
82.5°	73.8	68.4	62.2	56.9	53.8	49.2	47.6	44.6	44.6	43.8	43.8
85°	49.2	46.1	40.0	36.1	33.8	31.5	30.0	28.4	26.1	26.1	25.4
87.5°	26.1	24.6	23.0	18.4	18.4	16.1	15.4	14.6	12.3	13.1	13.1
90°	26.8	25.5	24.2	22.9	21.6	19.8	18.1	16.3	14.6	13.7	12.5
92.5°	25.8	24.5	23.2	21.9	20.6	18.8	17.1	15.3	13.6	12.7	12.9
95°	26.8	25.5	24.2	22.9	21.6	21.4	21.2	20.9	20.7	20.6	24.3
97.5°	26.0	24.9	23.8	22.7	21.6	44.4	67.3	90.1	113.0	124.4	122.0
100°	28.3	32.0	35.7	39.4	43.1	73.1	103.2	133.2	163.3	178.3	176.3
102.5°	52.9	101.9	150.9	199.9	248.9	246.3	243.7	241.0	238.4	237.1	235.8
105°	313.5	311.6	309.6	307.7	305.7	304.6	303.5	302.4	301.3	300.8	300.1
107.5°	372.8	371.7	370.6	369.5	368.4	366.9	365.3	363.8	362.3	361.5	361.2
110°	433.8	433.4	432.9	432.5	432.1	430.8	429.5	428.2	426.9	426.2	425.9

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	492.9	493.1	493.4	493.6	493.8	493.4	492.9	492.5	492.0	491.8	491.1
115°	554.3	553.9	553.4	553.0	552.6	552.8	553.0	553.2	553.4	553.5	553.2
117.5°	614.4	614.6	614.9	615.1	615.3	614.6	614.0	613.3	612.6	612.3	611.9
120°	671.9	671.4	671.0	670.5	670.1	670.3	670.5	670.8	671.0	671.1	670.7
122.5°	726.9	726.7	726.4	726.2	726.0	725.6	725.1	724.7	724.2	724.0	723.8
125°	778.6	777.9	777.2	776.6	775.9	776.3	776.8	777.2	777.7	777.9	777.5
127.5°	829.0	829.2	829.4	829.6	829.8	828.7	827.6	826.5	825.4	824.9	824.8
130°	876.8	876.6	876.3	876.1	875.9	875.2	874.6	873.9	873.2	872.9	872.8
132.5°	922.8	922.6	922.3	922.1	921.9	921.0	920.2	919.3	918.4	918.0	917.8
135°	964.8	964.4	963.9	963.5	963.1	962.2	961.4	960.5	959.6	959.2	959.3
137.5°	1006.0	1005.5	1005.1	1004.6	1004.2	1003.1	1002.0	1000.9	999.8	999.3	999.3
140°	1044.1	1043.4	1042.8	1042.1	1041.5	1041.1	1040.6	1040.2	1039.7	1039.5	1039.3
142.5°	1078.5	1078.0	1077.6	1077.1	1076.7	1076.5	1076.3	1076.0	1075.8	1075.7	1075.3
145°	1110.9	1110.7	1110.4	1110.2	1110.0	1110.0	1110.0	1110.0	1110.0	1110.0	1109.7
147.5°	1140.3	1140.1	1139.8	1139.6	1139.4	1139.6	1139.8	1140.1	1140.3	1140.4	1139.7
150°	1167.8	1167.8	1167.8	1167.8	1167.8	1168.0	1168.2	1168.5	1168.7	1168.8	1168.4
152.5°	1193.1	1192.7	1192.2	1191.8	1191.4	1191.8	1192.2	1192.7	1193.1	1193.3	1193.0
155°	1215.4	1214.5	1213.6	1212.8	1211.9	1212.6	1213.2	1213.9	1214.6	1214.9	1214.8
157.5°	1234.9	1233.8	1232.7	1231.6	1230.5	1231.4	1232.3	1233.2	1234.1	1234.5	1234.5
160°	1253.4	1252.1	1250.8	1249.5	1248.2	1248.4	1248.6	1248.9	1249.1	1249.2	1249.5
162.5°	1268.1	1266.8	1265.5	1264.2	1262.9	1263.1	1263.3	1263.6	1263.8	1263.9	1264.3
165°	1282.5	1280.8	1279.1	1277.3	1275.6	1275.6	1275.6	1275.6	1275.6	1275.6	1276.1
167.5°	1293.2	1291.3	1289.3	1287.4	1285.4	1285.6	1285.8	1286.1	1286.3	1286.4	1286.9
170°	1302.1	1300.4	1298.7	1296.9	1295.2	1295.0	1294.8	1294.5	1294.3	1294.2	1294.9
172.5°	1308.0	1306.3	1304.6	1302.8	1301.1	1300.9	1300.7	1300.4	1300.2	1300.1	1300.8
175°	1312.8	1310.9	1308.9	1307.0	1305.0	1304.8	1304.6	1304.3	1304.1	1304.0	1304.7
177.5°	1314.9	1313.2	1311.4	1309.7	1307.9	1307.5	1307.1	1306.6	1306.2	1306.0	1306.8
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9

TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	927.4	927.4	927.4	927.4
2.5°	902.0	909.7	916.6	927.4
5°	882.0	892.8	907.4	923.5
7.5°	859.0	875.9	895.1	917.4
10°	837.5	856.7	881.3	908.2
12.5°	815.2	838.2	865.1	894.3
15°	789.8	812.9	842.9	882.0
17.5°	766.8	794.4	826.7	868.2
20°	739.9	766.0	801.4	849.0
22.5°	716.1	746.0	785.2	826.7
25°	690.0	716.1	755.3	805.2
27.5°	663.8	696.1	733.7	782.2
30°	638.5	665.4	706.1	756.8
32.5°	610.8	643.1	680.7	728.4
35°	580.9	611.6	646.9	698.4
37.5°	554.0	583.9	620.0	665.4
40°	524.0	555.5	588.5	633.9
42.5°	494.8	523.2	556.3	597.8
45°	466.4	491.0	520.9	557.0
47.5°	437.2	457.9	485.6	517.8
50°	405.7	428.0	448.7	475.6
52.5°	376.5	395.7	412.6	434.9
55°	348.1	361.1	374.9	391.8
57.5°	318.1	328.1	338.1	355.7
60°	288.1	297.3	302.7	314.2
62.5°	258.9	262.8	269.7	276.6
65°	226.7	232.0	235.9	244.3
67.5°	197.5	199.8	203.6	209.0
70°	166.7	172.1	173.6	177.5
72.5°	140.6	142.9	144.4	145.2
75°	111.4	113.7	115.2	119.9
77.5°	87.6	86.8	89.9	90.7
80°	64.5	62.2	63.0	66.1
82.5°	42.3	43.0	42.3	42.3
85°	26.1	25.4	23.8	24.6
87.5°	11.5	11.5	10.8	10.8
90°	10.1	7.7	5.3	2.9
92.5°	13.4	13.8	14.3	14.7
95°	31.7	39.1	46.5	53.9
97.5°	117.2	112.5	107.7	102.9
100°	172.4	168.5	164.6	160.7
102.5°	233.2	230.5	227.9	225.3
105°	298.8	297.5	296.2	294.9
107.5°	360.5	359.9	359.2	358.6
110°	425.2	424.5	423.9	423.2



TEST NUMBER: P1013060

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	489.8	488.5	487.2	485.9
115°	552.5	551.9	551.2	550.6
117.5°	611.0	610.1	609.3	608.4
120°	669.8	668.9	668.1	667.2
122.5°	723.4	722.9	722.5	722.1
125°	776.6	775.7	774.9	774.0
127.5°	824.6	824.4	824.2	824.0
130°	872.6	872.4	872.2	872.0
132.5°	917.3	916.9	916.4	916.0
135°	959.5	959.7	959.9	960.1
137.5°	999.3	999.3	999.3	999.3
140°	1038.8	1038.4	1037.9	1037.5
142.5°	1074.4	1073.5	1072.7	1071.8
145°	1109.0	1108.4	1107.7	1107.1
147.5°	1138.4	1137.1	1135.8	1134.5
150°	1167.5	1166.6	1165.8	1164.9
152.5°	1192.3	1191.7	1191.0	1190.4
155°	1214.6	1214.3	1214.1	1213.9
157.5°	1234.5	1234.5	1234.5	1234.5
160°	1250.2	1250.8	1251.5	1252.1
162.5°	1265.2	1266.1	1266.9	1267.8
165°	1277.2	1278.3	1279.4	1280.5
167.5°	1288.0	1289.1	1290.2	1291.3
170°	1296.2	1297.5	1298.8	1300.1
172.5°	1302.1	1303.4	1304.7	1306.0
175°	1306.0	1307.3	1308.6	1309.9
177.5°	1308.3	1309.8	1311.3	1312.8
180°	1309.9	1309.9	1309.9	1309.9

(END OF REPORT)