

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013243

Luminaire Tested: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013243
REPORT IS A COMBINATION OF REPORTS P998986 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7472.0 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		102	102	102	102		88	88	88		75	75	75		63	63	63
1	100	96	92	89		93	90	86	83		78	75	73		67	65	64		57	56	54
2	92	84	78	73		85	79	74	69		69	65	61		59	56	54		51	49	47
3	84	75	67	62		78	70	64	59		61	56	52		53	49	46		45	43	40
4	77	66	59	53		72	62	55	50		55	49	45		47	43	40		41	38	35
5	71	59	51	46		66	56	49	43		49	43	39		43	38	35		37	34	31
6	65	53	45	40		61	50	43	38		44	39	34		39	34	31		34	30	27
7	61	48	41	35		56	46	39	34		40	35	30		35	31	27		31	27	25
8	56	44	36	31		53	42	35	30		37	31	27		33	28	25		28	25	22
9	53	40	33	28		49	38	31	27		34	28	24		30	25	22		26	23	20
10	49	37	30	25		46	35	29	24		31	26	22		28	23	20		24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13907	13907	13907	13907
5°	13906	15714	13929	12010
10°	13833	18114	13821	10445
15°	13667	20387	13667	8745
20°	13495	22104	13425	7701
25°	13286	22198	13224	6955
30°	13062	18876	12960	6442
35°	12745	14242	12584	6060
40°	12394	10322	12150	5762
45°	11812	7845	11519	5497
50°	11122	6340	10817	5110
55°	10375	5250	10036	4595
60°	9623	4439	9195	3821
65°	8682	3616	8406	3037
70°	7817	2933	7449	2467
75°	6850	2113	6374	1808
80°	5651	1401	5145	1330
85°	4097	721	3398	721

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 17409 cd/sqm

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.1	2.2
10°-20°	498.7	6.7
20°-30°	781.1	10.5
30°-40°	867.4	11.6
40°-50°	768.7	10.3
50°-60°	599.0	8.0
60°-70°	391.8	5.2
70°-80°	192.3	2.6
80°-90°	48.9	0.7
90°-100°	33.9	0.5
100°-110°	223.1	3.0
110°-120°	426.1	5.7
120°-130°	541.0	7.2
130°-140°	578.7	7.7
140°-150°	541.2	7.2
150°-160°	436.4	5.8
160°-170°	281.4	3.8
170°-180°	97.0	1.3
0°-30°	1445.0	19.3
0°-40°	2312.4	30.9
0°-60°	3680.1	49.3
0°-90°	4313.1	57.7
90°-120°	683.2	9.1
90°-150°	2344.0	31.4
90°-180°	3159.0	42.3
0°-180°	7472.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1705	1705	1705	1705	1705	
5°	1703	1971	1705	1506	1703	162
15°	1630	2611	1630	1120	1630	460
25°	1494	2816	1487	882	1494	688
35°	1303	1734	1286	738	1303	814
45°	1050	886	1024	621	1050	810
55°	756	529	731	463	756	676
65°	474	309	459	260	474	473
75°	238	143	221	122	238	252
85°	56	34	47	34	56	64
90°	2	23	2	23	2	6
95°	42	22	42	22	42	52
105°	230	218	230	218	230	241
115°	429	432	429	432	429	422
125°	603	608	603	608	603	539
135°	748	754	748	754	748	577
145°	863	867	863	867	863	539
155°	946	945	946	945	946	436
165°	998	993	998	993	998	282
175°	1021	1015	1021	1015	1021	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1708.1	1723.2	1731.5	1738.4	1752.1	1757.6	1768.6	1771.3	1782.3	1781.0	1776.8
5°	1702.6	1728.7	1748.0	1768.6	1793.3	1807.1	1822.2	1844.2	1855.2	1870.3	1879.9
7.5°	1693.0	1728.7	1760.3	1792.0	1831.8	1853.8	1873.0	1907.4	1936.2	1961.0	1988.5
10°	1677.9	1723.2	1770.0	1812.6	1867.5	1893.6	1922.5	1973.3	2013.2	2047.6	2091.5
12.5°	1654.5	1717.7	1770.0	1827.7	1897.8	1933.5	1972.0	2032.4	2079.2	2135.5	2190.5
15°	1629.8	1699.9	1768.6	1844.2	1923.9	1965.1	2003.6	2084.7	2156.1	2220.7	2281.2
17.5°	1602.3	1679.3	1754.9	1838.7	1934.9	1985.7	2031.1	2128.6	2207.0	2290.8	2351.3
20°	1569.3	1653.2	1739.7	1833.2	1941.7	1998.1	2048.9	2160.2	2246.8	2337.5	2413.1
22.5°	1533.6	1624.3	1719.1	1820.8	1933.5	1995.3	2054.4	2174.0	2274.3	2358.1	2459.8
25°	1493.8	1589.9	1687.5	1794.7	1921.1	1988.5	2048.9	2167.1	2274.3	2384.2	2483.2
27.5°	1452.5	1551.5	1653.2	1765.8	1895.0	1961.0	2029.7	2143.7	2268.8	2388.4	2488.7
30°	1407.2	1503.4	1610.6	1717.7	1855.2	1921.1	1991.2	2114.9	2250.9	2370.5	2479.1
32.5°	1357.7	1456.6	1558.3	1669.7	1804.3	1875.8	1940.4	2080.5	2219.3	2337.5	2439.2
35°	1302.7	1396.2	1492.4	1606.4	1739.7	1804.3	1881.3	2026.9	2167.1	2292.2	2358.1
37.5°	1243.6	1333.0	1422.3	1535.0	1662.8	1741.1	1816.7	1963.7	2112.1	2196.0	2230.3
40°	1188.7	1267.0	1345.3	1453.9	1583.1	1664.2	1741.1	1893.6	2024.2	2088.8	2062.7
42.5°	1118.6	1199.7	1269.8	1370.1	1500.6	1576.2	1654.5	1812.6	1918.4	1944.5	1879.9
45°	1049.9	1117.2	1184.6	1282.1	1419.5	1484.1	1568.0	1715.0	1802.9	1779.6	1684.8
47.5°	982.6	1037.5	1100.7	1195.6	1319.2	1396.2	1474.5	1602.3	1664.2	1631.2	1499.3
50°	902.8	957.8	1023.8	1106.2	1225.8	1300.0	1361.8	1480.0	1526.7	1445.7	1286.2
52.5°	827.3	875.4	931.7	1008.7	1122.7	1190.1	1257.4	1359.1	1374.2	1280.8	1113.1
55°	755.8	794.3	853.4	915.2	1019.7	1091.1	1137.8	1224.4	1220.3	1103.5	959.2
57.5°	681.6	717.3	757.2	821.8	920.7	974.3	1025.2	1100.7	1060.9	961.9	819.0
60°	615.6	636.3	676.1	737.9	821.8	868.5	908.3	949.6	915.2	808.0	698.1
62.5°	542.8	566.2	595.0	644.5	718.7	762.7	791.5	809.4	773.7	691.2	590.9
65°	474.1	494.7	524.9	568.9	625.3	658.2	673.4	685.7	666.5	573.0	493.3
67.5°	412.3	426.0	453.5	482.3	542.8	551.1	571.7	577.2	538.7	467.2	404.0
70°	350.4	364.2	376.5	410.9	438.4	453.5	457.6	457.6	419.1	372.4	320.2
72.5°	292.7	300.9	313.3	336.7	351.8	362.8	368.3	361.4	325.7	287.2	248.7
75°	237.7	241.9	252.9	268.0	280.3	276.2	274.8	266.6	240.5	213.0	191.0
77.5°	182.8	185.5	197.9	202.0	202.0	206.1	200.6	192.4	170.4	149.8	140.2
80°	137.4	141.5	142.9	145.7	142.9	142.9	138.8	125.1	114.1	104.4	97.6
82.5°	94.8	97.6	98.9	94.8	97.6	93.4	86.6	77.0	70.1	68.7	66.0
85°	56.3	57.7	56.3	56.3	52.2	50.8	45.3	44.0	41.2	41.2	39.9
87.5°	27.5	26.1	23.4	20.6	20.6	19.2	20.6	17.9	20.6	19.2	17.9
90°	2.3	4.2	6.0	7.9	9.8	10.7	11.4	12.7	14.1	15.4	16.8
92.5°	11.5	11.1	10.8	10.4	10.1	9.9	10.6	11.9	13.3	14.6	16.0
95°	42.0	36.2	30.4	24.7	18.9	16.0	16.1	16.3	16.4	16.6	16.8
97.5°	80.2	83.9	87.7	91.4	95.1	97.0	88.1	70.3	52.4	34.6	16.8
100°	125.2	128.3	131.3	134.4	137.5	139.0	127.3	103.9	80.4	57.0	33.6
102.5°	175.6	177.6	179.7	181.7	183.8	184.8	185.8	187.8	189.9	191.9	193.9
105°	229.8	230.8	231.8	232.9	233.9	234.4	234.8	235.7	236.5	237.4	238.2
107.5°	279.5	280.0	280.5	281.0	281.5	281.7	282.3	283.5	284.7	285.9	287.1
110°	329.9	330.4	330.9	331.4	331.9	332.1	332.6	333.6	334.7	335.7	336.7

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	378.7	379.7	380.7	381.8	382.8	383.3	383.5	383.8	384.1	384.5	384.8
115°	429.1	429.6	430.1	430.6	431.1	431.4	431.3	431.1	431.0	430.8	430.6
117.5°	474.2	474.9	475.5	476.2	476.9	477.2	477.5	478.0	478.5	479.0	479.5
120°	520.0	520.7	521.3	522.0	522.7	523.0	522.9	522.8	522.6	522.5	522.3
122.5°	562.7	563.1	563.4	563.8	564.1	564.3	564.5	564.8	565.1	565.5	565.8
125°	603.2	603.9	604.6	605.3	606.0	606.3	606.1	605.8	605.4	605.1	604.7
127.5°	642.1	642.3	642.5	642.6	642.8	642.9	643.3	644.2	645.0	645.9	646.7
130°	679.6	679.8	679.9	680.1	680.2	680.3	680.6	681.1	681.6	682.1	682.6
132.5°	713.9	714.2	714.6	714.9	715.2	715.4	715.7	716.4	717.1	717.8	718.5
135°	748.3	748.1	747.9	747.8	747.6	747.5	747.8	748.5	749.2	749.9	750.6
137.5°	778.8	778.8	778.8	778.8	778.8	778.8	779.2	780.1	780.9	781.8	782.6
140°	808.6	808.9	809.3	809.6	809.9	810.1	810.3	810.6	810.9	811.3	811.6
142.5°	835.3	836.0	836.7	837.4	838.1	838.4	838.5	838.6	838.8	838.9	839.1
145°	862.8	863.3	863.8	864.3	864.8	865.1	865.1	865.1	865.1	865.1	865.1
147.5°	884.2	885.2	886.2	887.3	888.3	888.8	888.7	888.5	888.4	888.2	888.0
150°	907.9	908.6	909.2	909.9	910.6	910.9	910.8	910.6	910.5	910.3	910.1
152.5°	927.7	928.2	928.7	929.2	929.7	930.0	929.8	929.5	929.2	928.8	928.5
155°	946.0	946.2	946.4	946.5	946.7	946.8	946.5	946.0	945.5	945.0	944.5
157.5°	962.1	962.1	962.1	962.1	962.1	962.1	961.8	961.1	960.4	959.7	959.0
160°	975.8	975.3	974.8	974.3	973.8	973.5	973.4	973.3	973.1	973.0	972.8
162.5°	988.0	987.3	986.7	986.0	985.3	985.0	984.9	984.7	984.6	984.4	984.2
165°	998.0	997.1	996.3	995.4	994.5	994.1	994.1	994.1	994.1	994.1	994.1
167.5°	1006.3	1005.5	1004.6	1003.8	1002.9	1002.5	1002.4	1002.3	1002.1	1002.0	1001.8
170°	1013.2	1012.2	1011.2	1010.1	1009.1	1008.6	1008.7	1008.9	1009.0	1009.2	1009.4
172.5°	1017.8	1016.8	1015.8	1014.7	1013.7	1013.2	1013.3	1013.5	1013.6	1013.8	1014.0
175°	1020.9	1019.9	1018.9	1017.8	1016.8	1016.3	1016.4	1016.5	1016.7	1016.8	1017.0
177.5°	1023.1	1021.9	1020.7	1019.6	1018.4	1017.8	1018.0	1018.3	1018.6	1019.0	1019.3
180°	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1787.8	1802.9	1804.3	1818.1	1813.9	1807.1	1819.4	1811.2	1827.7	1822.2	1829.1
5°	1892.3	1912.9	1930.7	1941.7	1961.0	1956.9	1977.5	1970.6	1985.7	1970.6	1989.8
7.5°	2014.6	2048.9	2066.8	2095.7	2103.9	2105.3	2130.0	2135.5	2145.1	2135.5	2146.5
10°	2134.1	2175.4	2216.6	2239.9	2255.1	2275.7	2297.7	2307.3	2314.1	2304.5	2311.4
12.5°	2242.7	2307.3	2352.6	2399.3	2410.3	2428.2	2451.6	2448.8	2476.3	2470.8	2483.2
15°	2343.0	2414.5	2469.4	2506.5	2536.8	2551.9	2595.9	2598.6	2597.2	2611.0	2602.7
17.5°	2432.3	2492.8	2571.1	2619.2	2656.3	2656.3	2681.1	2731.9	2727.8	2726.4	2734.7
20°	2505.2	2573.9	2646.7	2727.8	2758.0	2763.5	2797.9	2824.0	2828.1	2828.1	2828.1
22.5°	2560.1	2641.2	2719.5	2777.3	2800.6	2819.9	2850.1	2866.6	2872.1	2869.3	2872.1
25°	2587.6	2664.6	2744.3	2796.5	2810.2	2821.2	2824.0	2833.6	2832.2	2815.7	2825.4
27.5°	2593.1	2667.3	2719.5	2733.3	2726.4	2719.5	2675.6	2679.7	2667.3	2642.6	2652.2
30°	2568.4	2608.2	2606.9	2564.3	2551.9	2523.0	2483.2	2424.1	2376.0	2355.4	2362.2
32.5°	2479.1	2479.1	2429.6	2333.4	2290.8	2238.6	2167.1	2113.5	2050.3	2036.6	2062.7
35°	2355.4	2285.3	2194.6	2068.2	2003.6	1965.1	1841.4	1802.9	1749.4	1734.2	1746.6
37.5°	2163.0	2046.2	1914.3	1796.1	1741.1	1672.4	1563.8	1508.9	1470.4	1444.3	1456.6
40°	1947.2	1805.7	1668.3	1522.6	1462.1	1405.8	1324.7	1275.3	1213.4	1216.2	1220.3
42.5°	1741.1	1574.8	1420.9	1286.2	1228.5	1181.8	1125.5	1065.0	1043.0	1036.1	1029.3
45°	1522.6	1345.3	1201.0	1100.7	1048.5	1004.5	952.3	918.0	891.9	886.4	893.2
47.5°	1316.5	1166.7	1029.3	935.8	893.2	871.2	830.0	798.4	781.9	768.2	776.4
50°	1129.6	989.4	879.5	801.2	770.9	755.8	717.3	700.8	684.4	680.2	678.9
52.5°	975.7	856.1	761.3	698.1	674.7	666.5	637.6	614.3	600.5	604.6	607.4
55°	835.5	733.8	659.6	608.8	589.5	579.9	559.3	542.8	533.2	529.1	531.8
57.5°	711.8	623.9	570.3	529.1	514.0	509.8	487.8	482.3	475.5	471.3	471.3
60°	599.2	537.3	487.8	464.5	448.0	443.9	427.4	420.5	419.1	415.0	412.3
62.5°	504.3	453.5	419.1	394.4	387.5	386.1	375.2	366.9	362.8	360.0	360.0
65°	421.9	384.8	355.9	338.1	332.6	329.8	317.4	314.7	311.9	309.2	307.8
67.5°	351.8	318.8	298.2	285.8	279.0	280.3	273.5	268.0	268.0	266.6	265.2
70°	284.5	263.8	246.0	239.1	236.4	233.6	230.9	226.7	225.4	225.4	225.4
72.5°	224.0	210.3	200.6	196.5	193.8	191.0	188.3	188.3	188.3	186.9	186.9
75°	171.8	166.3	159.4	155.3	155.3	158.0	153.9	149.8	145.7	142.9	144.3
77.5°	129.2	126.4	122.3	115.4	116.8	114.1	114.1	111.3	112.7	112.7	109.9
80°	94.8	90.7	89.3	85.2	86.6	85.2	83.8	83.8	81.1	81.1	81.1
82.5°	66.0	61.8	61.8	60.5	59.1	59.1	57.7	57.7	59.1	56.3	56.3
85°	39.9	38.5	38.5	35.7	35.7	35.7	35.7	37.1	35.7	34.4	34.4
87.5°	17.9	19.2	17.9	16.5	16.5	16.5	15.1	15.1	13.7	15.1	15.1
90°	17.8	18.8	19.9	20.9	21.4	21.6	21.9	22.2	22.6	22.9	22.6
92.5°	17.0	18.0	19.1	20.1	20.6	20.6	20.6	20.6	20.6	20.6	20.6
95°	17.8	18.8	19.9	20.9	21.4	21.5	21.6	21.8	21.9	22.1	21.9
97.5°	17.6	18.5	19.3	20.2	20.6	20.7	20.9	21.0	21.2	21.4	21.2
100°	30.7	27.8	24.9	22.0	20.6	20.7	20.9	21.0	21.2	21.4	21.2
102.5°	155.7	117.5	79.4	41.2	22.1	22.1	22.1	22.1	22.1	22.1	22.1
105°	239.7	241.3	242.8	244.3	245.1	242.0	235.9	229.8	223.7	217.6	223.7
107.5°	287.9	288.8	289.6	290.5	290.9	291.2	291.9	292.6	293.3	294.0	293.3
110°	337.0	337.4	337.7	338.0	338.2	338.5	339.0	339.5	340.0	340.5	340.0

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	384.6	384.5	384.3	384.2	384.1	384.4	385.1	385.8	386.4	387.1	386.4
115°	431.0	431.3	431.7	432.0	432.2	432.2	432.2	432.2	432.2	432.2	432.2
117.5°	479.3	479.1	479.0	478.8	478.7	478.7	478.7	478.7	478.7	478.7	478.7
120°	522.6	523.0	523.3	523.6	523.8	523.6	523.3	523.0	522.6	522.3	522.6
122.5°	566.0	566.1	566.3	566.4	566.5	566.3	566.0	565.7	565.3	565.0	565.3
125°	605.2	605.7	606.2	606.7	607.0	607.1	607.3	607.4	607.6	607.8	607.6
127.5°	646.5	646.4	646.2	646.1	646.0	645.9	645.7	645.6	645.4	645.2	645.4
130°	682.8	683.0	683.1	683.3	683.4	683.4	683.4	683.4	683.4	683.4	683.4
132.5°	718.7	718.9	719.0	719.2	719.3	719.2	719.0	718.9	718.7	718.5	718.7
135°	750.9	751.3	751.6	751.9	752.1	752.3	752.6	752.9	753.3	753.6	753.3
137.5°	783.0	783.3	783.7	784.0	784.2	784.1	783.9	783.8	783.6	783.4	783.6
140°	812.1	812.6	813.1	813.6	813.9	814.0	814.2	814.3	814.5	814.7	814.5
142.5°	839.5	839.8	840.2	840.5	840.7	840.7	840.7	840.7	840.7	840.7	840.7
145°	865.3	865.5	865.6	865.8	865.9	866.1	866.4	866.7	867.1	867.4	867.1
147.5°	888.2	888.4	888.5	888.7	888.8	888.9	889.0	889.2	889.3	889.5	889.3
150°	910.1	910.1	910.1	910.1	910.1	910.2	910.4	910.5	910.7	910.9	910.7
152.5°	928.8	929.2	929.5	929.8	930.0	929.9	929.7	929.6	929.4	929.2	929.4
155°	945.2	945.9	946.6	947.3	947.6	947.3	946.8	946.3	945.8	945.3	945.8
157.5°	959.8	960.7	961.5	962.4	962.8	962.4	961.5	960.7	959.8	959.0	959.8
160°	973.8	974.8	975.8	976.8	977.3	976.8	975.8	974.8	973.8	972.8	973.8
162.5°	985.2	986.2	987.3	988.3	988.8	988.2	987.0	985.8	984.6	983.4	984.6
165°	995.5	996.8	998.2	999.5	1000.2	999.4	997.9	996.4	994.9	993.4	994.9
167.5°	1003.3	1004.8	1006.3	1007.8	1008.6	1007.8	1006.1	1004.4	1002.7	1001.0	1002.7
170°	1010.8	1012.1	1013.5	1014.8	1015.5	1014.7	1013.0	1011.3	1009.6	1007.9	1009.6
172.5°	1015.4	1016.7	1018.1	1019.4	1020.1	1019.2	1017.3	1015.4	1013.6	1011.7	1013.6
175°	1018.5	1020.1	1021.6	1023.1	1023.9	1022.9	1020.8	1018.8	1016.7	1014.7	1016.7
177.5°	1020.7	1022.0	1023.4	1024.7	1025.4	1024.4	1022.4	1020.3	1018.3	1016.3	1018.3
180°	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1833.2	1823.6	1822.2	1822.2	1807.1	1815.3	1798.8	1781.0	1772.7	1772.7	1757.6
5°	1985.7	1976.1	1966.5	1951.4	1951.4	1943.1	1917.0	1890.9	1871.7	1855.2	1837.3
7.5°	2142.4	2132.8	2105.3	2090.2	2098.4	2081.9	2047.6	2003.6	1970.6	1944.5	1907.4
10°	2312.8	2286.7	2272.9	2264.7	2235.8	2218.0	2178.1	2113.5	2072.3	2037.9	1989.8
12.5°	2451.6	2459.8	2407.6	2411.7	2382.9	2358.1	2296.3	2234.4	2172.6	2124.5	2053.1
15°	2601.4	2576.6	2545.0	2520.3	2510.7	2480.4	2428.2	2345.8	2278.4	2202.8	2121.8
17.5°	2719.5	2700.3	2670.1	2646.7	2626.1	2553.3	2509.3	2436.5	2344.4	2270.2	2171.2
20°	2819.9	2802.0	2759.4	2744.3	2707.2	2655.0	2591.7	2479.1	2396.6	2315.5	2219.3
22.5°	2862.5	2844.6	2807.5	2788.2	2764.9	2714.0	2653.6	2546.4	2444.7	2343.0	2241.3
25°	2826.7	2826.7	2808.9	2802.0	2781.4	2736.0	2674.2	2583.5	2474.9	2365.0	2244.1
27.5°	2653.6	2687.9	2700.3	2707.2	2707.2	2708.5	2665.9	2578.0	2472.2	2365.0	2238.6
30°	2403.5	2461.2	2512.0	2527.2	2553.3	2582.1	2600.0	2557.4	2462.6	2349.9	2223.5
32.5°	2088.8	2163.0	2257.8	2281.2	2316.9	2403.5	2451.6	2469.4	2417.2	2318.3	2183.6
35°	1775.5	1868.9	1926.6	1998.1	2031.1	2158.9	2266.1	2330.6	2318.3	2259.2	2136.9
37.5°	1502.0	1555.6	1625.7	1701.3	1767.2	1889.5	2022.8	2147.9	2198.7	2169.9	2077.8
40°	1239.5	1302.7	1386.6	1448.4	1493.8	1616.1	1781.0	1917.0	2028.3	2046.2	1989.8
42.5°	1054.0	1117.2	1168.1	1235.4	1271.1	1389.3	1535.0	1705.4	1837.3	1907.4	1882.7
45°	911.1	949.6	990.8	1029.3	1073.2	1177.7	1312.4	1499.3	1647.7	1746.6	1756.2
47.5°	786.0	820.4	856.1	891.9	916.6	997.7	1121.3	1273.9	1436.0	1572.1	1625.7
50°	698.1	714.6	740.7	761.3	790.2	860.2	959.2	1091.1	1262.9	1409.9	1480.0
52.5°	611.5	632.1	652.7	670.6	689.8	739.3	830.0	944.1	1092.5	1243.6	1330.2
55°	538.7	555.2	574.4	586.8	597.8	641.8	710.5	798.4	926.2	1069.1	1176.3
57.5°	479.6	486.5	503.0	509.8	522.2	557.9	607.4	685.7	788.8	927.6	1015.5
60°	415.0	428.7	441.1	446.6	456.2	481.0	515.3	588.2	677.5	779.2	879.5
62.5°	362.8	368.3	377.9	384.8	391.6	417.8	446.6	501.6	568.9	654.1	746.2
65°	314.7	317.4	322.9	332.6	336.7	355.9	372.4	412.3	475.5	540.1	632.1
67.5°	265.2	268.0	274.8	280.3	284.5	296.8	314.7	343.5	377.9	449.4	500.2
70°	226.7	226.7	230.9	233.6	237.7	243.2	252.9	274.8	306.4	351.8	398.5
72.5°	189.6	189.6	189.6	193.8	193.8	197.9	203.4	218.5	240.5	276.2	306.4
75°	147.0	148.4	151.2	151.2	152.5	158.0	162.2	166.3	177.3	200.6	228.1
77.5°	111.3	114.1	115.4	112.7	115.4	115.4	120.9	126.4	131.9	138.8	159.4
80°	82.5	83.8	81.1	82.5	82.5	85.2	87.9	86.6	89.3	97.6	103.1
82.5°	55.0	56.3	56.3	56.3	56.3	60.5	60.5	59.1	60.5	61.8	63.2
85°	34.4	33.0	33.0	34.4	33.0	33.0	34.4	35.7	34.4	35.7	37.1
87.5°	15.1	15.1	15.1	15.1	13.7	13.7	15.1	13.7	15.1	13.7	12.4
90°	22.2	21.9	21.6	21.4	20.9	19.9	18.8	17.8	16.8	15.4	14.1
92.5°	20.6	20.6	20.6	20.6	20.1	19.1	18.0	17.0	16.0	14.6	13.3
95°	21.8	21.6	21.5	21.4	20.9	19.9	18.8	17.8	16.8	16.6	16.4
97.5°	21.0	20.9	20.7	20.6	20.2	19.3	18.5	17.6	16.8	34.6	52.4
100°	21.0	20.9	20.7	20.6	22.0	24.9	27.8	30.7	33.6	57.0	80.4
102.5°	22.1	22.1	22.1	22.1	41.2	79.4	117.5	155.7	193.9	191.9	189.9
105°	229.8	235.9	242.0	245.1	244.3	242.8	241.3	239.7	238.2	237.4	236.5
107.5°	292.6	291.9	291.2	290.9	290.5	289.6	288.8	287.9	287.1	285.9	284.7
110°	339.5	339.0	338.5	338.2	338.0	337.7	337.4	337.0	336.7	335.7	334.7

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	385.8	385.1	384.4	384.1	384.2	384.3	384.5	384.6	384.8	384.5	384.1
115°	432.2	432.2	432.2	432.2	432.0	431.7	431.3	431.0	430.6	430.8	431.0
117.5°	478.7	478.7	478.7	478.7	478.8	479.0	479.1	479.3	479.5	479.0	478.5
120°	523.0	523.3	523.6	523.8	523.6	523.3	523.0	522.6	522.3	522.5	522.6
122.5°	565.7	566.0	566.3	566.5	566.4	566.3	566.1	566.0	565.8	565.5	565.1
125°	607.4	607.3	607.1	607.0	606.7	606.2	605.7	605.2	604.7	605.1	605.4
127.5°	645.6	645.7	645.9	646.0	646.1	646.2	646.4	646.5	646.7	645.9	645.0
130°	683.4	683.4	683.4	683.4	683.3	683.1	683.0	682.8	682.6	682.1	681.6
132.5°	718.9	719.0	719.2	719.3	719.2	719.0	718.9	718.7	718.5	717.8	717.1
135°	752.9	752.6	752.3	752.1	751.9	751.6	751.3	750.9	750.6	749.9	749.2
137.5°	783.8	783.9	784.1	784.2	784.0	783.7	783.3	783.0	782.6	781.8	780.9
140°	814.3	814.2	814.0	813.9	813.6	813.1	812.6	812.1	811.6	811.3	810.9
142.5°	840.7	840.7	840.7	840.7	840.5	840.2	839.8	839.5	839.1	838.9	838.8
145°	866.7	866.4	866.1	865.9	865.8	865.6	865.5	865.3	865.1	865.1	865.1
147.5°	889.2	889.0	888.9	888.8	888.7	888.5	888.4	888.2	888.0	888.2	888.4
150°	910.5	910.4	910.2	910.1	910.1	910.1	910.1	910.1	910.1	910.3	910.5
152.5°	929.6	929.7	929.9	930.0	929.8	929.5	929.2	928.8	928.5	928.8	929.2
155°	946.3	946.8	947.3	947.6	947.3	946.6	945.9	945.2	944.5	945.0	945.5
157.5°	960.7	961.5	962.4	962.8	962.4	961.5	960.7	959.8	959.0	959.7	960.4
160°	974.8	975.8	976.8	977.3	976.8	975.8	974.8	973.8	972.8	973.0	973.1
162.5°	985.8	987.0	988.2	988.8	988.3	987.3	986.2	985.2	984.2	984.4	984.6
165°	996.4	997.9	999.4	1000.2	999.5	998.2	996.8	995.5	994.1	994.1	994.1
167.5°	1004.4	1006.1	1007.8	1008.6	1007.8	1006.3	1004.8	1003.3	1001.8	1002.0	1002.1
170°	1011.3	1013.0	1014.7	1015.5	1014.8	1013.5	1012.1	1010.8	1009.4	1009.2	1009.0
172.5°	1015.4	1017.3	1019.2	1020.1	1019.4	1018.1	1016.7	1015.4	1014.0	1013.8	1013.6
175°	1018.8	1020.8	1022.9	1023.9	1023.1	1021.6	1020.1	1018.5	1017.0	1016.8	1016.7
177.5°	1020.3	1022.4	1024.4	1025.4	1024.7	1023.4	1022.0	1020.7	1019.3	1019.0	1018.6
180°	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1749.4	1742.5	1738.4	1737.0	1724.6	1717.7	1713.6	1710.9	1706.8	1695.8	1686.1
5°	1815.3	1796.1	1786.5	1775.5	1756.2	1734.2	1716.4	1705.4	1691.6	1669.7	1649.0
7.5°	1877.2	1848.3	1829.1	1813.9	1781.0	1745.2	1716.4	1693.0	1666.9	1636.7	1607.8
10°	1941.7	1895.0	1870.3	1846.9	1798.8	1752.1	1710.9	1676.5	1639.4	1599.6	1568.0
12.5°	1992.6	1930.7	1903.3	1870.3	1811.2	1756.2	1704.0	1657.3	1609.2	1566.6	1521.2
15°	2051.7	1974.7	1943.1	1900.5	1819.4	1748.0	1680.6	1629.8	1580.3	1517.1	1469.0
17.5°	2086.0	1996.7	1951.4	1914.3	1826.3	1739.7	1661.4	1598.2	1540.5	1477.3	1426.4
20°	2120.4	2018.7	1967.9	1915.6	1811.2	1719.1	1636.7	1561.1	1500.6	1431.9	1379.7
22.5°	2131.4	2013.2	1959.6	1911.5	1801.6	1698.5	1603.7	1526.7	1456.6	1387.9	1328.8
25°	2131.4	2011.8	1948.6	1886.8	1771.3	1665.5	1570.7	1486.9	1408.6	1339.8	1280.8
27.5°	2109.4	1984.3	1918.4	1862.0	1742.5	1628.4	1530.9	1438.8	1363.2	1294.5	1227.2
30°	2081.9	1944.5	1878.5	1811.2	1695.8	1587.2	1481.4	1396.2	1316.5	1238.2	1177.7
32.5°	2047.6	1901.9	1829.1	1760.3	1638.0	1525.4	1427.8	1344.0	1268.4	1187.3	1120.0
35°	1998.1	1838.7	1757.6	1697.1	1579.0	1462.1	1368.7	1286.2	1213.4	1129.6	1056.8
37.5°	1934.9	1781.0	1698.5	1624.3	1502.0	1394.8	1306.9	1227.2	1155.7	1078.7	997.7
40°	1860.7	1699.9	1628.4	1550.1	1420.9	1319.2	1236.8	1165.3	1093.9	1021.0	942.7
42.5°	1776.8	1617.4	1537.7	1462.1	1338.5	1238.2	1161.2	1096.6	1030.6	963.3	879.5
45°	1676.5	1526.7	1449.8	1378.3	1258.8	1155.7	1085.6	1023.8	967.4	898.7	824.5
47.5°	1563.8	1433.3	1355.0	1278.0	1161.2	1071.9	1003.2	950.9	902.8	834.1	766.8
50°	1453.9	1324.7	1261.5	1183.2	1076.0	992.2	922.1	878.1	841.0	773.7	713.2
52.5°	1315.1	1217.5	1157.1	1089.7	986.7	901.5	846.5	808.0	764.1	711.8	658.2
55°	1192.8	1102.1	1054.0	990.8	889.1	813.5	766.8	731.1	696.7	650.0	607.4
57.5°	1054.0	997.7	949.6	894.6	794.3	729.7	688.5	658.2	626.6	588.2	553.8
60°	908.3	882.2	835.5	791.5	706.3	650.0	615.6	588.2	557.9	526.3	497.5
62.5°	779.2	764.1	736.6	702.2	622.5	574.4	540.1	519.4	497.5	468.6	441.1
65°	656.9	650.0	623.9	599.2	544.2	501.6	471.3	459.0	434.2	412.3	387.5
67.5°	548.3	540.1	524.9	514.0	467.2	427.4	412.3	395.8	375.2	358.7	338.1
70°	438.4	437.0	427.4	413.6	388.9	360.0	344.9	333.9	313.3	300.9	285.8
72.5°	340.8	347.7	339.4	333.9	317.4	296.8	283.1	276.2	259.7	250.1	239.1
75°	254.2	259.7	263.8	254.2	250.1	240.5	228.1	221.2	213.0	199.3	195.1
77.5°	173.1	185.5	185.5	188.3	189.6	184.1	174.5	169.0	159.4	156.7	151.2
80°	114.1	125.1	126.4	129.2	133.3	133.3	126.4	125.1	115.4	114.1	109.9
82.5°	66.0	75.6	81.1	85.2	83.8	89.3	83.8	82.5	77.0	77.0	74.2
85°	35.7	37.1	39.9	42.6	45.3	48.1	48.1	46.7	45.3	44.0	41.2
87.5°	13.7	13.7	15.1	13.7	15.1	17.9	19.2	19.2	17.9	16.5	13.7
90°	12.7	11.4	10.7	9.8	7.9	6.0	4.2	2.3	4.2	6.0	7.9
92.5°	11.9	10.6	9.9	10.1	10.4	10.8	11.1	11.5	11.1	10.8	10.4
95°	16.3	16.1	16.0	18.9	24.7	30.4	36.2	42.0	36.2	30.4	24.7
97.5°	70.3	88.1	97.0	95.1	91.4	87.7	83.9	80.2	83.9	87.7	91.4
100°	103.9	127.3	139.0	137.5	134.4	131.3	128.3	125.2	128.3	131.3	134.4
102.5°	187.8	185.8	184.8	183.8	181.7	179.7	177.6	175.6	177.6	179.7	181.7
105°	235.7	234.8	234.4	233.9	232.9	231.8	230.8	229.8	230.8	231.8	232.9
107.5°	283.5	282.3	281.7	281.5	281.0	280.5	280.0	279.5	280.0	280.5	281.0
110°	333.6	332.6	332.1	331.9	331.4	330.9	330.4	329.9	330.4	330.9	331.4

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	383.8	383.5	383.3	382.8	381.8	380.7	379.7	378.7	379.7	380.7	381.8
115°	431.1	431.3	431.4	431.1	430.6	430.1	429.6	429.1	429.6	430.1	430.6
117.5°	478.0	477.5	477.2	476.9	476.2	475.5	474.9	474.2	474.9	475.5	476.2
120°	522.8	522.9	523.0	522.7	522.0	521.3	520.7	520.0	520.7	521.3	522.0
122.5°	564.8	564.5	564.3	564.1	563.8	563.4	563.1	562.7	563.1	563.4	563.8
125°	605.8	606.1	606.3	606.0	605.3	604.6	603.9	603.2	603.9	604.6	605.3
127.5°	644.2	643.3	642.9	642.8	642.6	642.5	642.3	642.1	642.3	642.5	642.6
130°	681.1	680.6	680.3	680.2	680.1	679.9	679.8	679.6	679.8	679.9	680.1
132.5°	716.4	715.7	715.4	715.2	714.9	714.6	714.2	713.9	714.2	714.6	714.9
135°	748.5	747.8	747.5	747.6	747.8	747.9	748.1	748.3	748.1	747.9	747.8
137.5°	780.1	779.2	778.8	778.8	778.8	778.8	778.8	778.8	778.8	778.8	778.8
140°	810.6	810.3	810.1	809.9	809.6	809.3	808.9	808.6	808.9	809.3	809.6
142.5°	838.6	838.5	838.4	838.1	837.4	836.7	836.0	835.3	836.0	836.7	837.4
145°	865.1	865.1	865.1	864.8	864.3	863.8	863.3	862.8	863.3	863.8	864.3
147.5°	888.5	888.7	888.8	888.3	887.3	886.2	885.2	884.2	885.2	886.2	887.3
150°	910.6	910.8	910.9	910.6	909.9	909.2	908.6	907.9	908.6	909.2	909.9
152.5°	929.5	929.8	930.0	929.7	929.2	928.7	928.2	927.7	928.2	928.7	929.2
155°	946.0	946.5	946.8	946.7	946.5	946.4	946.2	946.0	946.2	946.4	946.5
157.5°	961.1	961.8	962.1	962.1	962.1	962.1	962.1	962.1	962.1	962.1	962.1
160°	973.3	973.4	973.5	973.8	974.3	974.8	975.3	975.8	975.3	974.8	974.3
162.5°	984.7	984.9	985.0	985.3	986.0	986.7	987.3	988.0	987.3	986.7	986.0
165°	994.1	994.1	994.1	994.5	995.4	996.3	997.1	998.0	997.1	996.3	995.4
167.5°	1002.3	1002.4	1002.5	1002.9	1003.8	1004.6	1005.5	1006.3	1005.5	1004.6	1003.8
170°	1008.9	1008.7	1008.6	1009.1	1010.1	1011.2	1012.2	1013.2	1012.2	1011.2	1010.1
172.5°	1013.5	1013.3	1013.2	1013.7	1014.7	1015.8	1016.8	1017.8	1016.8	1015.8	1014.7
175°	1016.5	1016.4	1016.3	1016.8	1017.8	1018.9	1019.9	1020.9	1019.9	1018.9	1017.8
177.5°	1018.3	1018.0	1017.8	1018.4	1019.6	1020.7	1021.9	1023.1	1021.9	1020.7	1019.6
180°	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1677.9	1675.1	1672.4	1661.4	1651.8	1635.3	1621.6	1616.1	1614.7	1616.1	1611.9
5°	1629.8	1628.4	1618.8	1599.6	1581.7	1562.5	1548.7	1535.0	1526.7	1526.7	1517.1
7.5°	1584.5	1574.8	1566.6	1541.9	1521.2	1495.1	1474.5	1462.1	1455.3	1440.2	1440.2
10°	1536.4	1522.6	1511.6	1488.3	1458.0	1431.9	1405.8	1390.7	1378.3	1367.3	1363.2
12.5°	1488.3	1477.3	1456.6	1431.9	1401.7	1368.7	1341.2	1330.2	1301.4	1278.0	1279.4
15°	1442.9	1418.2	1408.6	1372.8	1337.1	1305.5	1265.6	1234.0	1210.7	1195.6	1176.3
17.5°	1392.1	1367.3	1349.5	1319.2	1272.5	1223.0	1184.6	1142.0	1118.6	1092.5	1080.1
20°	1335.7	1315.1	1301.4	1253.3	1196.9	1137.8	1095.2	1069.1	1043.0	1023.8	1012.8
22.5°	1287.6	1261.5	1245.0	1180.4	1118.6	1059.5	1026.5	1004.5	982.6	966.1	960.6
25°	1225.8	1210.7	1170.8	1114.5	1038.9	999.0	970.2	941.3	929.0	918.0	905.6
27.5°	1174.9	1137.8	1110.4	1036.1	989.4	944.1	915.2	893.2	878.1	867.1	857.5
30°	1111.7	1077.4	1038.9	977.1	934.5	891.9	865.7	847.9	831.4	824.5	816.3
32.5°	1045.8	1014.2	977.1	927.6	875.4	842.4	821.8	802.5	791.5	784.7	775.0
35°	986.7	946.8	922.1	875.4	832.8	795.7	776.4	759.9	747.6	744.8	743.4
37.5°	923.5	893.2	869.9	821.8	786.0	754.4	736.6	718.7	711.8	710.5	705.0
40°	868.5	842.4	820.4	775.0	736.6	707.7	694.0	683.0	676.1	676.1	674.7
42.5°	820.4	792.9	770.9	729.7	695.3	669.2	654.1	643.1	640.4	641.8	640.4
45°	766.8	743.4	721.5	678.9	650.0	630.8	614.3	608.8	604.6	606.0	607.4
47.5°	716.0	696.7	674.7	640.4	607.4	586.8	577.2	571.7	571.7	571.7	574.4
50°	670.6	648.6	629.4	593.7	563.4	546.9	538.7	531.8	533.2	534.6	535.9
52.5°	617.0	597.8	584.0	548.3	526.3	505.7	496.1	497.5	496.1	496.1	498.8
55°	570.3	551.1	537.3	504.3	482.3	468.6	460.4	456.2	457.6	454.9	460.4
57.5°	518.1	501.6	492.0	460.4	441.1	428.7	421.9	415.0	417.8	416.4	415.0
60°	472.7	453.5	438.4	416.4	399.9	384.8	380.7	373.8	376.5	373.8	372.4
62.5°	420.5	405.4	394.4	372.4	358.7	346.3	336.7	332.6	331.2	327.1	322.9
65°	368.3	360.0	349.0	327.1	313.3	303.7	298.2	294.1	292.7	281.7	269.3
67.5°	320.2	314.7	303.7	287.2	274.8	265.2	257.0	250.1	241.9	233.6	226.7
70°	274.8	266.6	259.7	244.6	233.6	224.0	215.7	207.5	203.4	195.1	192.4
72.5°	230.9	222.6	215.7	202.0	192.4	182.8	180.0	170.4	166.3	164.9	164.9
75°	185.5	178.6	174.5	162.2	153.9	147.0	142.9	140.2	137.4	134.7	130.5
77.5°	141.5	137.4	134.7	126.4	119.6	115.4	114.1	104.4	101.7	98.9	96.2
80°	103.1	101.7	98.9	92.1	89.3	79.7	79.7	77.0	75.6	75.6	75.6
82.5°	70.1	67.3	66.0	59.1	57.7	56.3	55.0	53.6	55.0	53.6	55.0
85°	37.1	35.7	34.4	34.4	34.4	34.4	34.4	34.4	34.4	33.0	34.4
87.5°	13.7	13.7	13.7	13.7	12.4	13.7	13.7	12.4	13.7	13.7	13.7
90°	9.8	10.7	11.4	12.7	14.1	15.4	16.8	17.8	18.8	19.9	20.9
92.5°	10.1	9.9	10.6	11.9	13.3	14.6	16.0	17.0	18.0	19.1	20.1
95°	18.9	16.0	16.1	16.3	16.4	16.6	16.8	17.8	18.8	19.9	20.9
97.5°	95.1	97.0	88.1	70.3	52.4	34.6	16.8	17.6	18.5	19.3	20.2
100°	137.5	139.0	127.3	103.9	80.4	57.0	33.6	30.7	27.8	24.9	22.0
102.5°	183.8	184.8	185.8	187.8	189.9	191.9	193.9	155.7	117.5	79.4	41.2
105°	233.9	234.4	234.8	235.7	236.5	237.4	238.2	239.7	241.3	242.8	244.3
107.5°	281.5	281.7	282.3	283.5	284.7	285.9	287.1	287.9	288.8	289.6	290.5
110°	331.9	332.1	332.6	333.6	334.7	335.7	336.7	337.0	337.4	337.7	338.0

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	382.8	383.3	383.5	383.8	384.1	384.5	384.8	384.6	384.5	384.3	384.2
115°	431.1	431.4	431.3	431.1	431.0	430.8	430.6	431.0	431.3	431.7	432.0
117.5°	476.9	477.2	477.5	478.0	478.5	479.0	479.5	479.3	479.1	479.0	478.8
120°	522.7	523.0	522.9	522.8	522.6	522.5	522.3	522.6	523.0	523.3	523.6
122.5°	564.1	564.3	564.5	564.8	565.1	565.5	565.8	566.0	566.1	566.3	566.4
125°	606.0	606.3	606.1	605.8	605.4	605.1	604.7	605.2	605.7	606.2	606.7
127.5°	642.8	642.9	643.3	644.2	645.0	645.9	646.7	646.5	646.4	646.2	646.1
130°	680.2	680.3	680.6	681.1	681.6	682.1	682.6	682.8	683.0	683.1	683.3
132.5°	715.2	715.4	715.7	716.4	717.1	717.8	718.5	718.7	718.9	719.0	719.2
135°	747.6	747.5	747.8	748.5	749.2	749.9	750.6	750.9	751.3	751.6	751.9
137.5°	778.8	778.8	779.2	780.1	780.9	781.8	782.6	783.0	783.3	783.7	784.0
140°	809.9	810.1	810.3	810.6	810.9	811.3	811.6	812.1	812.6	813.1	813.6
142.5°	838.1	838.4	838.5	838.6	838.8	838.9	839.1	839.5	839.8	840.2	840.5
145°	864.8	865.1	865.1	865.1	865.1	865.1	865.1	865.3	865.5	865.6	865.8
147.5°	888.3	888.8	888.7	888.5	888.4	888.2	888.0	888.2	888.4	888.5	888.7
150°	910.6	910.9	910.8	910.6	910.5	910.3	910.1	910.1	910.1	910.1	910.1
152.5°	929.7	930.0	929.8	929.5	929.2	928.8	928.5	928.8	929.2	929.5	929.8
155°	946.7	946.8	946.5	946.0	945.5	945.0	944.5	945.2	945.9	946.6	947.3
157.5°	962.1	962.1	961.8	961.1	960.4	959.7	959.0	959.8	960.7	961.5	962.4
160°	973.8	973.5	973.4	973.3	973.1	973.0	972.8	973.8	974.8	975.8	976.8
162.5°	985.3	985.0	984.9	984.7	984.6	984.4	984.2	985.2	986.2	987.3	988.3
165°	994.5	994.1	994.1	994.1	994.1	994.1	994.1	995.5	996.8	998.2	999.5
167.5°	1002.9	1002.5	1002.4	1002.3	1002.1	1002.0	1001.8	1003.3	1004.8	1006.3	1007.8
170°	1009.1	1008.6	1008.7	1008.9	1009.0	1009.2	1009.4	1010.8	1012.1	1013.5	1014.8
172.5°	1013.7	1013.2	1013.3	1013.5	1013.6	1013.8	1014.0	1015.4	1016.7	1018.1	1019.4
175°	1016.8	1016.3	1016.4	1016.5	1016.7	1016.8	1017.0	1018.5	1020.1	1021.6	1023.1
177.5°	1018.4	1017.8	1018.0	1018.3	1018.6	1019.0	1019.3	1020.7	1022.0	1023.4	1024.7
180°	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1611.9	1617.4	1610.6	1614.7	1605.1	1603.7	1605.1	1605.1	1606.4	1607.8	1609.2
5°	1521.2	1519.9	1511.6	1506.1	1502.0	1506.1	1508.9	1511.6	1508.9	1511.6	1513.0
7.5°	1436.0	1431.9	1427.8	1418.2	1420.9	1418.2	1426.4	1422.3	1422.3	1429.2	1434.7
10°	1360.5	1352.2	1349.5	1338.5	1330.2	1328.8	1338.5	1342.6	1346.7	1349.5	1360.5
12.5°	1262.9	1250.5	1240.9	1245.0	1221.7	1231.3	1234.0	1228.5	1245.0	1264.3	1253.3
15°	1158.4	1159.8	1140.6	1133.7	1114.5	1120.0	1121.3	1135.1	1148.8	1147.5	1163.9
17.5°	1081.5	1073.2	1056.8	1055.4	1047.1	1051.3	1049.9	1060.9	1056.8	1063.6	1077.4
20°	1010.0	1004.5	990.8	985.3	988.0	985.3	986.7	988.0	992.2	1007.3	1004.5
22.5°	953.7	946.8	946.8	940.0	931.7	929.0	935.8	940.0	945.4	948.2	955.1
25°	904.2	898.7	891.9	887.7	880.9	882.2	886.4	891.9	896.0	901.5	907.0
27.5°	853.4	853.4	846.5	845.1	842.4	841.0	846.5	849.3	849.3	853.4	858.9
30°	813.5	813.5	806.7	805.3	803.9	803.9	808.0	809.4	810.8	814.9	817.6
32.5°	775.0	773.7	770.9	772.3	770.9	772.3	772.3	773.7	776.4	777.8	783.3
35°	739.3	740.7	737.9	737.9	736.6	737.9	740.7	742.1	743.4	746.2	746.2
37.5°	705.0	707.7	706.3	710.5	710.5	710.5	710.5	713.2	713.2	713.2	711.8
40°	674.7	674.7	673.4	676.1	678.9	678.9	680.2	680.2	681.6	681.6	680.2
42.5°	640.4	643.1	647.2	648.6	651.4	650.0	654.1	652.7	654.1	651.4	648.6
45°	608.8	608.8	614.3	619.8	621.1	621.1	621.1	623.9	621.1	617.0	615.6
47.5°	574.4	577.2	579.9	586.8	588.2	588.2	588.2	588.2	585.4	585.4	585.4
50°	540.1	541.4	542.8	545.6	549.7	548.3	548.3	548.3	553.8	548.3	549.7
52.5°	498.8	500.2	501.6	507.1	505.7	505.7	507.1	507.1	511.2	509.8	507.1
55°	457.6	457.6	460.4	460.4	460.4	463.1	464.5	467.2	465.9	467.2	468.6
57.5°	416.4	413.6	412.3	412.3	416.4	415.0	416.4	416.4	421.9	424.6	426.0
60°	368.3	368.3	366.9	358.7	358.7	357.3	361.4	364.2	366.9	379.3	377.9
62.5°	318.8	313.3	307.8	309.2	300.9	305.1	302.3	305.1	313.3	322.9	324.3
65°	269.3	265.2	259.7	258.3	255.6	259.7	258.3	259.7	263.8	269.3	276.2
67.5°	225.4	224.0	221.2	219.9	219.9	219.9	222.6	222.6	224.0	228.1	232.2
70°	192.4	191.0	192.4	189.6	191.0	189.6	191.0	192.4	193.8	195.1	199.3
72.5°	162.2	162.2	162.2	159.4	162.2	160.8	160.8	162.2	163.5	164.9	167.7
75°	129.2	126.4	123.7	120.9	119.6	122.3	123.7	122.3	126.4	131.9	131.9
77.5°	97.6	96.2	96.2	96.2	97.6	96.2	98.9	97.6	98.9	98.9	101.7
80°	75.6	74.2	75.6	75.6	74.2	77.0	75.6	75.6	77.0	78.3	77.0
82.5°	55.0	56.3	55.0	55.0	55.0	57.7	55.0	55.0	55.0	56.3	56.3
85°	34.4	34.4	34.4	34.4	35.7	34.4	35.7	34.4	37.1	35.7	35.7
87.5°	12.4	13.7	15.1	15.1	15.1	15.1	13.7	15.1	16.5	15.1	16.5
90°	21.4	21.6	21.9	22.2	22.6	22.9	22.6	22.2	21.9	21.6	21.4
92.5°	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6
95°	21.4	21.5	21.6	21.8	21.9	22.1	21.9	21.8	21.6	21.5	21.4
97.5°	20.6	20.7	20.9	21.0	21.2	21.4	21.2	21.0	20.9	20.7	20.6
100°	20.6	20.7	20.9	21.0	21.2	21.4	21.2	21.0	20.9	20.7	20.6
102.5°	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1
105°	245.1	242.0	235.9	229.8	223.7	217.6	223.7	229.8	235.9	242.0	245.1
107.5°	290.9	291.2	291.9	292.6	293.3	294.0	293.3	292.6	291.9	291.2	290.9
110°	338.2	338.5	339.0	339.5	340.0	340.5	340.0	339.5	339.0	338.5	338.2

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	384.1	384.4	385.1	385.8	386.4	387.1	386.4	385.8	385.1	384.4	384.1
115°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
117.5°	478.7	478.7	478.7	478.7	478.7	478.7	478.7	478.7	478.7	478.7	478.7
120°	523.8	523.6	523.3	523.0	522.6	522.3	522.6	523.0	523.3	523.6	523.8
122.5°	566.5	566.3	566.0	565.7	565.3	565.0	565.3	565.7	566.0	566.3	566.5
125°	607.0	607.1	607.3	607.4	607.6	607.8	607.6	607.4	607.3	607.1	607.0
127.5°	646.0	645.9	645.7	645.6	645.4	645.2	645.4	645.6	645.7	645.9	646.0
130°	683.4	683.4	683.4	683.4	683.4	683.4	683.4	683.4	683.4	683.4	683.4
132.5°	719.3	719.2	719.0	718.9	718.7	718.5	718.7	718.9	719.0	719.2	719.3
135°	752.1	752.3	752.6	752.9	753.3	753.6	753.3	752.9	752.6	752.3	752.1
137.5°	784.2	784.1	783.9	783.8	783.6	783.4	783.6	783.8	783.9	784.1	784.2
140°	813.9	814.0	814.2	814.3	814.5	814.7	814.5	814.3	814.2	814.0	813.9
142.5°	840.7	840.7	840.7	840.7	840.7	840.7	840.7	840.7	840.7	840.7	840.7
145°	865.9	866.1	866.4	866.7	867.1	867.4	867.1	866.7	866.4	866.1	865.9
147.5°	888.8	888.9	889.0	889.2	889.3	889.5	889.3	889.2	889.0	888.9	888.8
150°	910.1	910.2	910.4	910.5	910.7	910.9	910.7	910.5	910.4	910.2	910.1
152.5°	930.0	929.9	929.7	929.6	929.4	929.2	929.4	929.6	929.7	929.9	930.0
155°	947.6	947.3	946.8	946.3	945.8	945.3	945.8	946.3	946.8	947.3	947.6
157.5°	962.8	962.4	961.5	960.7	959.8	959.0	959.8	960.7	961.5	962.4	962.8
160°	977.3	976.8	975.8	974.8	973.8	972.8	973.8	974.8	975.8	976.8	977.3
162.5°	988.8	988.2	987.0	985.8	984.6	983.4	984.6	985.8	987.0	988.2	988.8
165°	1000.2	999.4	997.9	996.4	994.9	993.4	994.9	996.4	997.9	999.4	1000.2
167.5°	1008.6	1007.8	1006.1	1004.4	1002.7	1001.0	1002.7	1004.4	1006.1	1007.8	1008.6
170°	1015.5	1014.7	1013.0	1011.3	1009.6	1007.9	1009.6	1011.3	1013.0	1014.7	1015.5
172.5°	1020.1	1019.2	1017.3	1015.4	1013.6	1011.7	1013.6	1015.4	1017.3	1019.2	1020.1
175°	1023.9	1022.9	1020.8	1018.8	1016.7	1014.7	1016.7	1018.8	1020.8	1022.9	1023.9
177.5°	1025.4	1024.4	1022.4	1020.3	1018.3	1016.3	1018.3	1020.3	1022.4	1024.4	1025.4
180°	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1614.7	1621.6	1618.8	1609.2	1613.3	1621.6	1629.8	1640.8	1647.7	1653.2	1655.9
5°	1519.9	1532.2	1529.5	1529.5	1535.0	1548.7	1562.5	1585.8	1594.1	1603.7	1617.4
7.5°	1436.0	1445.7	1453.9	1456.6	1464.9	1482.8	1500.6	1526.7	1547.3	1558.3	1566.6
10°	1361.8	1368.7	1381.1	1387.9	1396.2	1418.2	1444.3	1471.8	1492.4	1511.6	1522.6
12.5°	1267.0	1294.5	1311.0	1322.0	1333.0	1366.0	1386.6	1416.8	1441.5	1459.4	1475.9
15°	1161.2	1194.2	1203.8	1246.4	1273.9	1300.0	1331.6	1367.3	1390.7	1411.3	1433.3
17.5°	1071.9	1095.2	1106.2	1151.6	1174.9	1216.2	1261.5	1306.9	1342.6	1357.7	1379.7
20°	1015.5	1027.9	1049.9	1065.0	1089.7	1137.8	1187.3	1242.3	1295.9	1311.0	1333.0
22.5°	957.8	974.3	989.4	1010.0	1029.3	1062.3	1111.7	1172.2	1229.9	1257.4	1283.5
25°	905.6	922.1	931.7	953.7	971.6	1004.5	1038.9	1100.7	1169.4	1192.8	1234.0
27.5°	864.4	874.0	890.5	900.1	920.7	950.9	982.6	1029.3	1096.6	1136.5	1176.3
30°	823.1	830.0	843.8	857.5	872.6	893.2	929.0	974.3	1036.1	1070.5	1110.4
32.5°	781.9	792.9	801.2	810.8	827.3	852.0	876.7	920.7	970.2	1008.7	1048.5
35°	747.6	751.7	762.7	773.7	784.7	806.7	832.8	875.4	919.3	949.6	985.3
37.5°	710.5	717.3	725.6	729.7	747.6	761.3	788.8	821.8	874.0	893.2	929.0
40°	681.6	680.2	688.5	695.3	703.6	725.6	742.1	777.8	819.0	849.3	871.2
42.5°	645.9	645.9	648.6	656.9	667.9	681.6	700.8	731.1	773.7	795.7	821.8
45°	617.0	612.9	614.3	619.8	626.6	640.4	659.6	685.7	728.3	746.2	773.7
47.5°	582.7	578.5	578.5	584.0	589.5	599.2	614.3	644.5	678.9	702.2	722.8
50°	544.2	545.6	544.2	548.3	551.1	560.7	577.2	601.9	633.5	652.7	676.1
52.5°	508.5	505.7	504.3	507.1	512.6	519.4	537.3	559.3	589.5	608.8	629.4
55°	464.5	467.2	467.2	467.2	475.5	478.2	492.0	514.0	544.2	559.3	578.5
57.5°	424.6	423.3	426.0	424.6	431.5	441.1	452.1	468.6	498.8	514.0	531.8
60°	380.7	382.0	383.4	383.4	388.9	398.5	410.9	426.0	450.7	465.9	482.3
62.5°	327.1	333.9	340.8	343.5	351.8	358.7	366.9	383.4	405.4	416.4	431.5
65°	276.2	285.8	295.5	302.3	307.8	314.7	325.7	340.8	358.7	369.7	384.8
67.5°	232.2	239.1	251.5	258.3	269.3	277.6	284.5	296.8	318.8	322.9	335.3
70°	200.6	203.4	208.9	214.4	226.7	233.6	241.9	254.2	270.7	280.3	287.2
72.5°	169.0	170.4	173.1	178.6	184.1	192.4	202.0	213.0	228.1	232.2	241.9
75°	134.7	142.9	142.9	147.0	151.2	155.3	163.5	174.5	184.1	191.0	196.5
77.5°	100.3	104.4	107.2	114.1	119.6	123.7	129.2	137.4	142.9	148.4	152.5
80°	78.3	79.7	81.1	81.1	83.8	89.3	94.8	100.3	107.2	109.9	114.1
82.5°	57.7	57.7	57.7	60.5	61.8	63.2	63.2	66.0	72.8	75.6	79.7
85°	37.1	37.1	37.1	37.1	38.5	39.9	41.2	42.6	42.6	42.6	45.3
87.5°	15.1	17.9	16.5	17.9	17.9	17.9	17.9	19.2	19.2	20.6	20.6
90°	20.9	19.9	18.8	17.8	16.8	15.4	14.1	12.7	11.4	10.7	9.8
92.5°	20.1	19.1	18.0	17.0	16.0	14.6	13.3	11.9	10.6	9.9	10.1
95°	20.9	19.9	18.8	17.8	16.8	16.6	16.4	16.3	16.1	16.0	18.9
97.5°	20.2	19.3	18.5	17.6	16.8	34.6	52.4	70.3	88.1	97.0	95.1
100°	22.0	24.9	27.8	30.7	33.6	57.0	80.4	103.9	127.3	139.0	137.5
102.5°	41.2	79.4	117.5	155.7	193.9	191.9	189.9	187.8	185.8	184.8	183.8
105°	244.3	242.8	241.3	239.7	238.2	237.4	236.5	235.7	234.8	234.4	233.9
107.5°	290.5	289.6	288.8	287.9	287.1	285.9	284.7	283.5	282.3	281.7	281.5
110°	338.0	337.7	337.4	337.0	336.7	335.7	334.7	333.6	332.6	332.1	331.9

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	384.2	384.3	384.5	384.6	384.8	384.5	384.1	383.8	383.5	383.3	382.8
115°	432.0	431.7	431.3	431.0	430.6	430.8	431.0	431.1	431.3	431.4	431.1
117.5°	478.8	479.0	479.1	479.3	479.5	479.0	478.5	478.0	477.5	477.2	476.9
120°	523.6	523.3	523.0	522.6	522.3	522.5	522.6	522.8	522.9	523.0	522.7
122.5°	566.4	566.3	566.1	566.0	565.8	565.5	565.1	564.8	564.5	564.3	564.1
125°	606.7	606.2	605.7	605.2	604.7	605.1	605.4	605.8	606.1	606.3	606.0
127.5°	646.1	646.2	646.4	646.5	646.7	645.9	645.0	644.2	643.3	642.9	642.8
130°	683.3	683.1	683.0	682.8	682.6	682.1	681.6	681.1	680.6	680.3	680.2
132.5°	719.2	719.0	718.9	718.7	718.5	717.8	717.1	716.4	715.7	715.4	715.2
135°	751.9	751.6	751.3	750.9	750.6	749.9	749.2	748.5	747.8	747.5	747.6
137.5°	784.0	783.7	783.3	783.0	782.6	781.8	780.9	780.1	779.2	778.8	778.8
140°	813.6	813.1	812.6	812.1	811.6	811.3	810.9	810.6	810.3	810.1	809.9
142.5°	840.5	840.2	839.8	839.5	839.1	838.9	838.8	838.6	838.5	838.4	838.1
145°	865.8	865.6	865.5	865.3	865.1	865.1	865.1	865.1	865.1	865.1	864.8
147.5°	888.7	888.5	888.4	888.2	888.0	888.2	888.4	888.5	888.7	888.8	888.3
150°	910.1	910.1	910.1	910.1	910.1	910.3	910.5	910.6	910.8	910.9	910.6
152.5°	929.8	929.5	929.2	928.8	928.5	928.8	929.2	929.5	929.8	930.0	929.7
155°	947.3	946.6	945.9	945.2	944.5	945.0	945.5	946.0	946.5	946.8	946.7
157.5°	962.4	961.5	960.7	959.8	959.0	959.7	960.4	961.1	961.8	962.1	962.1
160°	976.8	975.8	974.8	973.8	972.8	973.0	973.1	973.3	973.4	973.5	973.8
162.5°	988.3	987.3	986.2	985.2	984.2	984.4	984.6	984.7	984.9	985.0	985.3
165°	999.5	998.2	996.8	995.5	994.1	994.1	994.1	994.1	994.1	994.1	994.5
167.5°	1007.8	1006.3	1004.8	1003.3	1001.8	1002.0	1002.1	1002.3	1002.4	1002.5	1002.9
170°	1014.8	1013.5	1012.1	1010.8	1009.4	1009.2	1009.0	1008.9	1008.7	1008.6	1009.1
172.5°	1019.4	1018.1	1016.7	1015.4	1014.0	1013.8	1013.6	1013.5	1013.3	1013.2	1013.7
175°	1023.1	1021.6	1020.1	1018.5	1017.0	1016.8	1016.7	1016.5	1016.4	1016.3	1016.8
177.5°	1024.7	1023.4	1022.0	1020.7	1019.3	1019.0	1018.6	1018.3	1018.0	1017.8	1018.4
180°	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1705.4	1705.4	1705.4	1705.4
2.5°	1666.9	1675.1	1688.9	1708.1
5°	1628.4	1651.8	1673.8	1702.6
7.5°	1594.1	1621.6	1651.8	1693.0
10°	1554.2	1588.6	1627.1	1677.9
12.5°	1507.5	1555.6	1599.6	1654.5
15°	1473.1	1508.9	1565.2	1629.8
17.5°	1425.0	1473.1	1529.5	1602.3
20°	1379.7	1430.5	1493.8	1569.3
22.5°	1331.6	1389.3	1452.5	1533.6
25°	1282.1	1344.0	1407.2	1493.8
27.5°	1236.8	1293.1	1364.6	1452.5
30°	1181.8	1246.4	1315.1	1407.2
32.5°	1128.2	1195.6	1265.6	1357.7
35°	1070.5	1137.8	1214.8	1302.7
37.5°	1014.2	1088.4	1158.4	1243.6
40°	952.3	1029.3	1102.1	1188.7
42.5°	891.9	971.6	1044.4	1118.6
45°	835.5	913.8	979.8	1049.9
47.5°	781.9	852.0	919.3	982.6
50°	729.7	788.8	850.6	902.8
52.5°	674.7	731.1	780.5	827.3
55°	625.3	669.2	713.2	755.8
57.5°	566.2	610.1	648.6	681.6
60°	516.7	544.2	581.3	615.6
62.5°	460.4	492.0	520.8	542.8
65°	405.4	432.9	454.9	474.1
67.5°	358.7	375.2	391.6	412.3
70°	302.3	316.1	335.3	350.4
72.5°	254.2	265.2	274.8	292.7
75°	206.1	215.7	221.2	237.7
77.5°	159.4	169.0	173.1	182.8
80°	122.3	123.7	129.2	137.4
82.5°	83.8	86.6	87.9	94.8
85°	48.1	55.0	53.6	56.3
87.5°	20.6	22.0	24.7	27.5
90°	7.9	6.0	4.2	2.3
92.5°	10.4	10.8	11.1	11.5
95°	24.7	30.4	36.2	42.0
97.5°	91.4	87.7	83.9	80.2
100°	134.4	131.3	128.3	125.2
102.5°	181.7	179.7	177.6	175.6
105°	232.9	231.8	230.8	229.8
107.5°	281.0	280.5	280.0	279.5
110°	331.4	330.9	330.4	329.9

TEST NUMBER: P1013243

CATALOG NUMBER: S124RDIP-B1020D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	381.8	380.7	379.7	378.7
115°	430.6	430.1	429.6	429.1
117.5°	476.2	475.5	474.9	474.2
120°	522.0	521.3	520.7	520.0
122.5°	563.8	563.4	563.1	562.7
125°	605.3	604.6	603.9	603.2
127.5°	642.6	642.5	642.3	642.1
130°	680.1	679.9	679.8	679.6
132.5°	714.9	714.6	714.2	713.9
135°	747.8	747.9	748.1	748.3
137.5°	778.8	778.8	778.8	778.8
140°	809.6	809.3	808.9	808.6
142.5°	837.4	836.7	836.0	835.3
145°	864.3	863.8	863.3	862.8
147.5°	887.3	886.2	885.2	884.2
150°	909.9	909.2	908.6	907.9
152.5°	929.2	928.7	928.2	927.7
155°	946.5	946.4	946.2	946.0
157.5°	962.1	962.1	962.1	962.1
160°	974.3	974.8	975.3	975.8
162.5°	986.0	986.7	987.3	988.0
165°	995.4	996.3	997.1	998.0
167.5°	1003.8	1004.6	1005.5	1006.3
170°	1010.1	1011.2	1012.2	1013.2
172.5°	1014.7	1015.8	1016.8	1017.8
175°	1017.8	1018.9	1019.9	1020.9
177.5°	1019.6	1020.7	1021.9	1023.1
180°	1020.9	1020.9	1020.9	1020.9

(END OF REPORT)