

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013303

Luminaire Tested: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013303
REPORT IS A COMBINATION OF REPORTS P999228 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5505.0 lumens
Efficiency: N/A
Efficacy: 132.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26			
1	93	89	85	82	83	79	76	73	62	60	58	45	44	43	31	30	29	23			
2	85	78	72	67	75	69	65	61	54	51	48	40	38	36	27	26	25	19			
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	22	17			
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	14			
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13			
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	14	11			
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10			
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	12	9			
9	47	36	29	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8			
10	44	33	26	21	39	30	24	19	24	19	16	18	15	13	13	11	9	7			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4636	4636	4636	4636
5°	4635	5238	4643	4003
10°	4611	6038	4607	3481
15°	4556	6795	4556	2915
20°	4498	7368	4475	2567
25°	4428	7399	4408	2319
30°	4354	6292	4320	2148
35°	4248	4748	4194	2020
40°	4131	3441	4050	1921
45°	3938	2615	3840	1832
50°	3707	2113	3606	1704
55°	3458	1750	3345	1532
60°	3208	1479	3065	1274
65°	2894	1206	2802	1013
70°	2606	977	2483	822
75°	2282	704	2124	603
80°	1884	466	1715	444
85°	1368	241	1135	241

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 5803 cd/sqm

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.0	1.0
10°-20°	166.2	3.0
20°-30°	260.4	4.7
30°-40°	289.1	5.3
40°-50°	256.2	4.7
50°-60°	199.7	3.6
60°-70°	130.6	2.4
70°-80°	64.1	1.2
80°-90°	18.3	0.3
90°-100°	43.6	0.8
100°-110°	287.2	5.2
110°-120°	548.4	10.0
120°-130°	696.2	12.6
130°-140°	744.8	13.5
140°-150°	696.4	12.7
150°-160°	561.6	10.2
160°-170°	362.2	6.6
170°-180°	124.8	2.3
0°-30°	481.7	8.7
0°-40°	770.8	14.0
0°-60°	1226.7	22.3
0°-90°	1439.7	26.2
90°-120°	879.2	16.0
90°-150°	3016.6	54.8
90°-180°	4065.0	73.8
0°-180°	5505.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	568	568	568	568	568	
5°	568	657	568	502	568	54
15°	543	870	543	373	543	153
25°	498	939	496	294	498	229
35°	434	578	429	246	434	271
45°	350	296	341	207	350	270
55°	252	176	244	154	252	225
65°	158	103	153	87	158	158
75°	79	48	74	41	79	84
85°	19	12	16	12	19	21
90°	3	30	3	30	3	4
95°	54	28	54	28	54	67
105°	296	280	296	280	296	310
115°	552	556	552	556	552	544
125°	776	782	776	782	776	693
135°	963	970	963	970	963	742
145°	1110	1116	1110	1116	1110	694
155°	1218	1216	1218	1216	1218	561
165°	1284	1278	1284	1278	1284	363
175°	1314	1306	1314	1306	1314	125
180°	1314	1314	1314	1314	1314	

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	569.4	574.4	577.2	579.5	584.0	585.9	589.5	590.4	594.1	593.7	592.3
5°	567.5	576.2	582.7	589.5	597.8	602.4	607.4	614.7	618.4	623.4	626.6
7.5°	564.3	576.2	586.8	597.3	610.6	617.9	624.3	635.8	645.4	653.7	662.8
10°	559.3	574.4	590.0	604.2	622.5	631.2	640.8	657.8	671.1	682.5	697.2
12.5°	551.5	572.6	590.0	609.2	632.6	644.5	657.3	677.5	693.1	711.8	730.2
15°	543.3	566.6	589.5	614.7	641.3	655.0	667.9	694.9	718.7	740.2	760.4
17.5°	534.1	559.8	585.0	612.9	645.0	661.9	677.0	709.5	735.7	763.6	783.8
20°	523.1	551.1	579.9	611.1	647.2	666.0	683.0	720.1	748.9	779.2	804.4
22.5°	511.2	541.4	573.0	606.9	644.5	665.1	684.8	724.7	758.1	786.0	819.9
25°	497.9	530.0	562.5	598.2	640.4	662.8	683.0	722.4	758.1	794.7	827.7
27.5°	484.2	517.2	551.1	588.6	631.7	653.7	676.6	714.6	756.3	796.1	829.6
30°	469.1	501.1	536.9	572.6	618.4	640.4	663.7	705.0	750.3	790.2	826.4
32.5°	452.6	485.5	519.4	556.6	601.4	625.3	646.8	693.5	739.8	779.2	813.1
35°	434.2	465.4	497.5	535.5	579.9	601.4	627.1	675.6	722.4	764.1	786.0
37.5°	414.5	444.3	474.1	511.7	554.3	580.4	605.6	654.6	704.0	732.0	743.4
40°	396.2	422.3	448.4	484.6	527.7	554.7	580.4	631.2	674.7	696.3	687.6
42.5°	372.9	399.9	423.3	456.7	500.2	525.4	551.5	604.2	639.5	648.2	626.6
45°	350.0	372.4	394.9	427.4	473.2	494.7	522.7	571.7	601.0	593.2	561.6
47.5°	327.5	345.8	366.9	398.5	439.7	465.4	491.5	534.1	554.7	543.7	499.8
50°	300.9	319.3	341.3	368.7	408.6	433.3	453.9	493.3	508.9	481.9	428.7
52.5°	275.8	291.8	310.6	336.2	374.2	396.7	419.1	453.0	458.1	426.9	371.0
55°	251.9	264.8	284.5	305.1	339.9	363.7	379.3	408.1	406.8	367.8	319.7
57.5°	227.2	239.1	252.4	273.9	306.9	324.8	341.7	366.9	353.6	320.6	273.0
60°	205.2	212.1	225.4	246.0	273.9	289.5	302.8	316.5	305.1	269.3	232.7
62.5°	180.9	188.7	198.3	214.8	239.6	254.2	263.8	269.8	257.9	230.4	197.0
65°	158.0	164.9	175.0	189.6	208.4	219.4	224.5	228.6	222.2	191.0	164.4
67.5°	137.4	142.0	151.2	160.8	180.9	183.7	190.6	192.4	179.6	155.7	134.7
70°	116.8	121.4	125.5	137.0	146.1	151.2	152.5	152.5	139.7	124.1	106.7
72.5°	97.6	100.3	104.4	112.2	117.3	120.9	122.8	120.5	108.6	95.7	82.9
75°	79.2	80.6	84.3	89.3	93.4	92.1	91.6	88.9	80.2	71.0	63.7
77.5°	60.9	61.8	66.0	67.3	67.3	68.7	66.9	64.1	56.8	49.9	46.7
80°	45.8	47.2	47.6	48.6	47.6	47.6	46.3	41.7	38.0	34.8	32.5
82.5°	31.6	32.5	33.0	31.6	32.5	31.1	28.9	25.7	23.4	22.9	22.0
85°	18.8	19.2	18.8	18.8	17.4	16.9	15.1	14.7	13.7	13.7	13.3
87.5°	9.2	8.7	7.8	6.9	6.9	6.4	6.9	6.0	6.9	6.4	6.0
90°	2.9	5.3	7.7	10.2	12.6	13.8	14.7	16.4	18.1	19.9	21.6
92.5°	14.7	14.3	13.9	13.4	13.0	12.8	13.7	15.4	17.1	18.9	20.6
95°	54.0	46.6	39.2	31.7	24.3	20.6	20.7	20.9	21.2	21.4	21.6
97.5°	103.2	108.0	112.8	117.6	122.4	124.8	113.3	90.4	67.5	44.5	21.6
100°	161.2	165.1	169.0	172.9	176.8	178.8	163.7	133.6	103.5	73.3	43.2
102.5°	226.0	228.6	231.2	233.9	236.5	237.8	239.1	241.7	244.4	247.0	249.6
105°	295.8	297.1	298.4	299.7	301.0	301.7	302.2	303.3	304.4	305.5	306.6
107.5°	359.6	360.3	360.9	361.6	362.3	362.6	363.4	364.9	366.4	368.0	369.5
110°	424.5	425.1	425.8	426.4	427.1	427.4	428.1	429.4	430.7	432.0	433.3

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	487.4	488.7	490.0	491.3	492.6	493.3	493.5	493.9	494.4	494.8	495.2
115°	552.2	552.9	553.5	554.2	554.9	555.2	555.1	554.9	554.6	554.4	554.2
117.5°	610.2	611.1	611.9	612.8	613.7	614.1	614.4	615.1	615.8	616.4	617.1
120°	669.2	670.1	670.9	671.8	672.7	673.1	673.0	672.8	672.5	672.3	672.1
122.5°	724.2	724.6	725.1	725.5	726.0	726.2	726.4	726.8	727.3	727.7	728.1
125°	776.3	777.2	778.0	778.9	779.8	780.2	780.0	779.5	779.1	778.6	778.2
127.5°	826.4	826.6	826.8	827.1	827.3	827.4	827.9	829.0	830.1	831.2	832.3
130°	874.5	874.7	874.9	875.2	875.4	875.5	875.8	876.5	877.2	877.8	878.5
132.5°	918.8	919.2	919.6	920.1	920.5	920.7	921.1	922.0	922.9	923.8	924.7
135°	963.0	962.8	962.6	962.3	962.1	962.0	962.4	963.3	964.2	965.0	965.9
137.5°	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.8	1003.9	1005.0	1006.1	1007.2
140°	1040.6	1041.0	1041.5	1041.9	1042.4	1042.6	1042.8	1043.2	1043.7	1044.1	1044.5
142.5°	1075.0	1075.9	1076.7	1077.6	1078.5	1078.9	1079.0	1079.2	1079.5	1079.7	1079.9
145°	1110.4	1111.0	1111.7	1112.3	1113.0	1113.3	1113.3	1113.3	1113.3	1113.3	1113.3
147.5°	1137.9	1139.2	1140.5	1141.8	1143.1	1143.8	1143.7	1143.5	1143.2	1143.0	1142.8
150°	1168.3	1169.2	1170.1	1171.0	1171.9	1172.3	1172.2	1172.0	1171.7	1171.5	1171.3
152.5°	1193.9	1194.5	1195.2	1195.8	1196.5	1196.8	1196.6	1196.2	1195.7	1195.3	1194.9
155°	1217.5	1217.7	1217.9	1218.2	1218.4	1218.5	1218.2	1217.5	1216.8	1216.2	1215.5
157.5°	1238.1	1238.1	1238.1	1238.1	1238.1	1238.1	1237.7	1236.8	1235.9	1235.1	1234.2
160°	1255.8	1255.2	1254.5	1253.9	1253.2	1252.9	1252.8	1252.6	1252.3	1252.1	1251.9
162.5°	1271.5	1270.6	1269.8	1268.9	1268.0	1267.6	1267.5	1267.3	1267.0	1266.8	1266.6
165°	1284.3	1283.2	1282.1	1281.0	1279.9	1279.4	1279.4	1279.4	1279.4	1279.4	1279.4
167.5°	1295.1	1294.0	1292.9	1291.8	1290.7	1290.2	1290.1	1289.9	1289.6	1289.4	1289.2
170°	1303.9	1302.6	1301.3	1300.0	1298.7	1298.1	1298.2	1298.4	1298.6	1298.8	1299.0
172.5°	1309.8	1308.5	1307.2	1305.9	1304.6	1303.9	1304.0	1304.2	1304.5	1304.7	1304.9
175°	1313.8	1312.5	1311.2	1309.9	1308.6	1307.9	1308.0	1308.2	1308.5	1308.7	1308.9
177.5°	1316.7	1315.2	1313.6	1312.1	1310.6	1309.8	1310.0	1310.5	1310.9	1311.4	1311.8
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	595.9	601.0	601.4	606.0	604.6	602.4	606.5	603.7	609.2	607.4	609.7
5°	630.8	637.6	643.6	647.2	653.7	652.3	659.2	656.9	661.9	656.9	663.3
7.5°	671.5	683.0	688.9	698.6	701.3	701.8	710.0	711.8	715.0	711.8	715.5
10°	711.4	725.1	738.9	746.6	751.7	758.6	765.9	769.1	771.4	768.2	770.5
12.5°	747.6	769.1	784.2	799.8	803.4	809.4	817.2	816.3	825.4	823.6	827.7
15°	781.0	804.8	823.1	835.5	845.6	850.6	865.3	866.2	865.7	870.3	867.6
17.5°	810.8	830.9	857.0	873.1	885.4	885.4	893.7	910.6	909.3	908.8	911.6
20°	835.1	858.0	882.2	909.3	919.3	921.2	932.6	941.3	942.7	942.7	942.7
22.5°	853.4	880.4	906.5	925.8	933.5	940.0	950.0	955.5	957.4	956.4	957.4
25°	862.5	888.2	914.8	932.2	936.7	940.4	941.3	944.5	944.1	938.6	941.8
27.5°	864.4	889.1	906.5	911.1	908.8	906.5	891.9	893.2	889.1	880.9	884.1
30°	856.1	869.4	869.0	854.8	850.6	841.0	827.7	808.0	792.0	785.1	787.4
32.5°	826.4	826.4	809.9	777.8	763.6	746.2	722.4	704.5	683.4	678.9	687.6
35°	785.1	761.8	731.5	689.4	667.9	655.0	613.8	601.0	583.1	578.1	582.2
37.5°	721.0	682.1	638.1	598.7	580.4	557.5	521.3	503.0	490.1	481.4	485.5
40°	649.1	601.9	556.1	507.5	487.4	468.6	441.6	425.1	404.5	405.4	406.8
42.5°	580.4	524.9	473.6	428.7	409.5	393.9	375.2	355.0	347.7	345.4	343.1
45°	507.5	448.4	400.3	366.9	349.5	334.8	317.4	306.0	297.3	295.5	297.7
47.5°	438.8	388.9	343.1	311.9	297.7	290.4	276.7	266.1	260.6	256.1	258.8
50°	376.5	329.8	293.2	267.1	257.0	251.9	239.1	233.6	228.1	226.7	226.3
52.5°	325.2	285.4	253.8	232.7	224.9	222.2	212.5	204.8	200.2	201.5	202.5
55°	278.5	244.6	219.9	202.9	196.5	193.3	186.4	180.9	177.7	176.4	177.3
57.5°	237.3	208.0	190.1	176.4	171.3	169.9	162.6	160.8	158.5	157.1	157.1
60°	199.7	179.1	162.6	154.8	149.3	148.0	142.5	140.2	139.7	138.3	137.4
62.5°	168.1	151.2	139.7	131.5	129.2	128.7	125.1	122.3	120.9	120.0	120.0
65°	140.6	128.3	118.6	112.7	110.9	109.9	105.8	104.9	104.0	103.1	102.6
67.5°	117.3	106.3	99.4	95.3	93.0	93.4	91.2	89.3	89.3	88.9	88.4
70°	94.8	87.9	82.0	79.7	78.8	77.9	77.0	75.6	75.1	75.1	75.1
72.5°	74.7	70.1	66.9	65.5	64.6	63.7	62.8	62.8	62.8	62.3	62.3
75°	57.3	55.4	53.1	51.8	51.8	52.7	51.3	49.9	48.6	47.6	48.1
77.5°	43.1	42.1	40.8	38.5	38.9	38.0	38.0	37.1	37.6	37.6	36.6
80°	31.6	30.2	29.8	28.4	28.9	28.4	27.9	27.9	27.0	27.0	27.0
82.5°	22.0	20.6	20.6	20.2	19.7	19.7	19.2	19.2	19.7	18.8	18.8
85°	13.3	12.8	12.8	11.9	11.9	11.9	11.9	12.4	11.9	11.5	11.5
87.5°	6.0	6.4	6.0	5.5	5.5	5.5	5.0	5.0	4.6	5.0	5.0
90°	22.9	24.2	25.5	26.8	27.5	27.7	28.2	28.6	29.1	29.5	29.1
92.5°	21.9	23.2	24.5	25.8	26.5	26.5	26.5	26.5	26.5	26.5	26.5
95°	22.9	24.2	25.5	26.8	27.5	27.6	27.8	28.1	28.3	28.5	28.3
97.5°	22.7	23.8	24.9	26.0	26.5	26.6	26.8	27.1	27.3	27.5	27.3
100°	39.5	35.8	32.1	28.4	26.5	26.6	26.8	27.1	27.3	27.5	27.3
102.5°	200.5	151.3	102.2	53.1	28.5	28.5	28.5	28.5	28.5	28.5	28.5
105°	308.6	310.5	312.5	314.4	315.4	311.5	303.6	295.7	287.9	280.0	287.9
107.5°	370.6	371.7	372.8	373.9	374.4	374.8	375.7	376.6	377.4	378.3	377.4
110°	433.7	434.2	434.6	435.1	435.3	435.6	436.3	437.0	437.6	438.3	437.6

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	495.0	494.8	494.6	494.4	494.3	494.7	495.6	496.5	497.3	498.2	497.3
115°	554.6	555.1	555.5	556.0	556.2	556.2	556.2	556.2	556.2	556.2	556.2
117.5°	616.9	616.7	616.4	616.2	616.1	616.1	616.1	616.1	616.1	616.1	616.1
120°	672.5	673.0	673.4	673.9	674.1	673.9	673.4	673.0	672.5	672.1	672.5
122.5°	728.3	728.5	728.8	729.0	729.1	728.9	728.4	728.0	727.5	727.1	727.5
125°	778.9	779.5	780.2	780.9	781.2	781.3	781.5	781.8	782.0	782.2	782.0
127.5°	832.1	831.9	831.6	831.4	831.3	831.2	831.0	830.7	830.5	830.3	830.5
130°	878.7	878.9	879.2	879.4	879.5	879.5	879.5	879.5	879.5	879.5	879.5
132.5°	924.9	925.1	925.3	925.5	925.6	925.5	925.3	925.1	924.9	924.7	924.9
135°	966.3	966.8	967.2	967.7	967.9	968.1	968.6	969.0	969.5	969.9	969.5
137.5°	1007.6	1008.1	1008.5	1009.0	1009.2	1009.1	1008.9	1008.6	1008.4	1008.2	1008.4
140°	1045.2	1045.8	1046.5	1047.2	1047.5	1047.6	1047.8	1048.1	1048.3	1048.5	1048.3
142.5°	1080.3	1080.8	1081.2	1081.7	1081.9	1081.9	1081.9	1081.9	1081.9	1081.9	1081.9
145°	1113.5	1113.7	1114.0	1114.2	1114.3	1114.5	1115.0	1115.4	1115.9	1116.3	1115.9
147.5°	1143.0	1143.2	1143.5	1143.7	1143.8	1143.9	1144.1	1144.4	1144.6	1144.8	1144.6
150°	1171.3	1171.3	1171.3	1171.3	1171.3	1171.4	1171.6	1171.9	1172.1	1172.3	1172.1
152.5°	1195.3	1195.7	1196.2	1196.6	1196.8	1196.7	1196.5	1196.3	1196.1	1195.9	1196.1
155°	1216.4	1217.2	1218.1	1219.0	1219.4	1219.1	1218.4	1217.8	1217.1	1216.5	1217.1
157.5°	1235.3	1236.4	1237.5	1238.6	1239.1	1238.6	1237.5	1236.4	1235.3	1234.2	1235.3
160°	1253.2	1254.5	1255.8	1257.1	1257.8	1257.1	1255.8	1254.5	1253.2	1251.9	1253.2
162.5°	1267.9	1269.2	1270.5	1271.8	1272.5	1271.7	1270.2	1268.7	1267.1	1265.6	1267.1
165°	1281.1	1282.9	1284.6	1286.3	1287.2	1286.2	1284.3	1282.3	1280.4	1278.4	1280.4
167.5°	1291.2	1293.2	1295.1	1297.1	1298.1	1297.0	1294.8	1292.6	1290.4	1288.2	1290.4
170°	1300.8	1302.5	1304.3	1306.0	1306.9	1305.8	1303.6	1301.5	1299.3	1297.1	1299.3
172.5°	1306.7	1308.4	1310.2	1311.9	1312.8	1311.6	1309.2	1306.8	1304.4	1302.0	1304.4
175°	1310.9	1312.8	1314.8	1316.7	1317.7	1316.4	1313.8	1311.1	1308.5	1305.9	1308.5
177.5°	1313.6	1315.3	1317.1	1318.8	1319.7	1318.4	1315.8	1313.1	1310.5	1307.9	1310.5
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	611.1	607.9	607.4	607.4	602.4	605.1	599.6	593.7	590.9	590.9	585.9
5°	661.9	658.7	655.5	650.5	650.5	647.7	639.0	630.3	623.9	618.4	612.4
7.5°	714.1	710.9	701.8	696.7	699.5	694.0	682.5	667.9	656.9	648.2	635.8
10°	770.9	762.2	757.6	754.9	745.3	739.3	726.0	704.5	690.8	679.3	663.3
12.5°	817.2	819.9	802.5	803.9	794.3	786.0	765.4	744.8	724.2	708.2	684.4
15°	867.1	858.9	848.3	840.1	836.9	826.8	809.4	781.9	759.5	734.3	707.3
17.5°	906.5	900.1	890.0	882.2	875.4	851.1	836.4	812.2	781.5	756.7	723.7
20°	940.0	934.0	919.8	914.8	902.4	885.0	863.9	826.4	798.9	771.8	739.8
22.5°	954.2	948.2	935.8	929.4	921.6	904.7	884.5	848.8	814.9	781.0	747.1
25°	942.2	942.2	936.3	934.0	927.1	912.0	891.4	861.2	825.0	788.3	748.0
27.5°	884.5	896.0	900.1	902.4	902.4	902.8	888.6	859.3	824.1	788.3	746.2
30°	801.2	820.4	837.3	842.4	851.1	860.7	866.7	852.5	820.9	783.3	741.2
32.5°	696.3	721.0	752.6	760.4	772.3	801.2	817.2	823.1	805.7	772.8	727.9
35°	591.8	623.0	642.2	666.0	677.0	719.6	755.4	776.9	772.8	753.1	712.3
37.5°	500.7	518.5	541.9	567.1	589.1	629.8	674.3	716.0	732.9	723.3	692.6
40°	413.2	434.2	462.2	482.8	497.9	538.7	593.7	639.0	676.1	682.1	663.3
42.5°	351.3	372.4	389.4	411.8	423.7	463.1	511.7	568.5	612.4	635.8	627.6
45°	303.7	316.5	330.3	343.1	357.7	392.6	437.5	499.8	549.2	582.2	585.4
47.5°	262.0	273.5	285.4	297.3	305.5	332.6	373.8	424.6	478.7	524.0	541.9
50°	232.7	238.2	246.9	253.8	263.4	286.7	319.7	363.7	421.0	470.0	493.3
52.5°	203.8	210.7	217.6	223.5	229.9	246.4	276.7	314.7	364.2	414.5	443.4
55°	179.6	185.1	191.5	195.6	199.3	213.9	236.8	266.1	308.7	356.4	392.1
57.5°	159.9	162.2	167.7	169.9	174.1	186.0	202.5	228.6	262.9	309.2	338.5
60°	138.3	142.9	147.0	148.9	152.1	160.3	171.8	196.1	225.8	259.7	293.2
62.5°	120.9	122.8	126.0	128.3	130.5	139.3	148.9	167.2	189.6	218.0	248.7
65°	104.9	105.8	107.6	110.9	112.2	118.6	124.1	137.4	158.5	180.0	210.7
67.5°	88.4	89.3	91.6	93.4	94.8	98.9	104.9	114.5	126.0	149.8	166.7
70°	75.6	75.6	77.0	77.9	79.2	81.1	84.3	91.6	102.1	117.3	132.8
72.5°	63.2	63.2	63.2	64.6	64.6	66.0	67.8	72.8	80.2	92.1	102.1
75°	49.0	49.5	50.4	50.4	50.8	52.7	54.1	55.4	59.1	66.9	76.0
77.5°	37.1	38.0	38.5	37.6	38.5	38.5	40.3	42.1	44.0	46.3	53.1
80°	27.5	27.9	27.0	27.5	27.5	28.4	29.3	28.9	29.8	32.5	34.4
82.5°	18.3	18.8	18.8	18.8	18.8	20.2	20.2	19.7	20.2	20.6	21.1
85°	11.5	11.0	11.0	11.5	11.0	11.0	11.5	11.9	11.5	11.9	12.4
87.5°	5.0	5.0	5.0	5.0	4.6	4.6	5.0	4.6	5.0	4.6	4.1
90°	28.6	28.2	27.7	27.5	26.8	25.5	24.2	22.9	21.6	19.9	18.1
92.5°	26.5	26.5	26.5	26.5	25.8	24.5	23.2	21.9	20.6	18.9	17.1
95°	28.1	27.8	27.6	27.5	26.8	25.5	24.2	22.9	21.6	21.4	21.2
97.5°	27.1	26.8	26.6	26.5	26.0	24.9	23.8	22.7	21.6	44.5	67.5
100°	27.1	26.8	26.6	26.5	28.4	32.1	35.8	39.5	43.2	73.3	103.5
102.5°	28.5	28.5	28.5	28.5	53.1	102.2	151.3	200.5	249.6	247.0	244.4
105°	295.7	303.6	311.5	315.4	314.4	312.5	310.5	308.6	306.6	305.5	304.4
107.5°	376.6	375.7	374.8	374.4	373.9	372.8	371.7	370.6	369.5	368.0	366.4
110°	437.0	436.3	435.6	435.3	435.1	434.6	434.2	433.7	433.3	432.0	430.7

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	496.5	495.6	494.7	494.3	494.4	494.6	494.8	495.0	495.2	494.8	494.4
115°	556.2	556.2	556.2	556.2	556.0	555.5	555.1	554.6	554.2	554.4	554.6
117.5°	616.1	616.1	616.1	616.1	616.2	616.4	616.7	616.9	617.1	616.4	615.8
120°	673.0	673.4	673.9	674.1	673.9	673.4	673.0	672.5	672.1	672.3	672.5
122.5°	728.0	728.4	728.9	729.1	729.0	728.8	728.5	728.3	728.1	727.7	727.3
125°	781.8	781.5	781.3	781.2	780.9	780.2	779.5	778.9	778.2	778.6	779.1
127.5°	830.7	831.0	831.2	831.3	831.4	831.6	831.9	832.1	832.3	831.2	830.1
130°	879.5	879.5	879.5	879.5	879.4	879.2	878.9	878.7	878.5	877.8	877.2
132.5°	925.1	925.3	925.5	925.6	925.5	925.3	925.1	924.9	924.7	923.8	922.9
135°	969.0	968.6	968.1	967.9	967.7	967.2	966.8	966.3	965.9	965.0	964.2
137.5°	1008.6	1008.9	1009.1	1009.2	1009.0	1008.5	1008.1	1007.6	1007.2	1006.1	1005.0
140°	1048.1	1047.8	1047.6	1047.5	1047.2	1046.5	1045.8	1045.2	1044.5	1044.1	1043.7
142.5°	1081.9	1081.9	1081.9	1081.9	1081.7	1081.2	1080.8	1080.3	1079.9	1079.7	1079.5
145°	1115.4	1115.0	1114.5	1114.3	1114.2	1114.0	1113.7	1113.5	1113.3	1113.3	1113.3
147.5°	1144.4	1144.1	1143.9	1143.8	1143.7	1143.5	1143.2	1143.0	1142.8	1143.0	1143.2
150°	1171.9	1171.6	1171.4	1171.3	1171.3	1171.3	1171.3	1171.3	1171.3	1171.5	1171.7
152.5°	1196.3	1196.5	1196.7	1196.8	1196.6	1196.2	1195.7	1195.3	1194.9	1195.3	1195.7
155°	1217.8	1218.4	1219.1	1219.4	1219.0	1218.1	1217.2	1216.4	1215.5	1216.2	1216.8
157.5°	1236.4	1237.5	1238.6	1239.1	1238.6	1237.5	1236.4	1235.3	1234.2	1235.1	1235.9
160°	1254.5	1255.8	1257.1	1257.8	1257.1	1255.8	1254.5	1253.2	1251.9	1252.1	1252.3
162.5°	1268.7	1270.2	1271.7	1272.5	1271.8	1270.5	1269.2	1267.9	1266.6	1266.8	1267.0
165°	1282.3	1284.3	1286.2	1287.2	1286.3	1284.6	1282.9	1281.1	1279.4	1279.4	1279.4
167.5°	1292.6	1294.8	1297.0	1298.1	1297.1	1295.1	1293.2	1291.2	1289.2	1289.4	1289.6
170°	1301.5	1303.6	1305.8	1306.9	1306.0	1304.3	1302.5	1300.8	1299.0	1298.8	1298.6
172.5°	1306.8	1309.2	1311.6	1312.8	1311.9	1310.2	1308.4	1306.7	1304.9	1304.7	1304.5
175°	1311.1	1313.8	1316.4	1317.7	1316.7	1314.8	1312.8	1310.9	1308.9	1308.7	1308.5
177.5°	1313.1	1315.8	1318.4	1319.7	1318.8	1317.1	1315.3	1313.6	1311.8	1311.4	1310.9
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	583.1	580.8	579.5	579.0	574.9	572.6	571.2	570.3	568.9	565.3	562.0
5°	605.1	598.7	595.5	591.8	585.4	578.1	572.1	568.5	563.9	556.6	549.7
7.5°	625.7	616.1	609.7	604.6	593.7	581.7	572.1	564.3	555.6	545.6	535.9
10°	647.2	631.7	623.4	615.6	599.6	584.0	570.3	558.8	546.5	533.2	522.7
12.5°	664.2	643.6	634.4	623.4	603.7	585.4	568.0	552.4	536.4	522.2	507.1
15°	683.9	658.2	647.7	633.5	606.5	582.7	560.2	543.3	526.8	505.7	489.7
17.5°	695.3	665.6	650.5	638.1	608.8	579.9	553.8	532.7	513.5	492.4	475.5
20°	706.8	672.9	656.0	638.5	603.7	573.0	545.6	520.4	500.2	477.3	459.9
22.5°	710.5	671.1	653.2	637.2	600.5	566.2	534.6	508.9	485.5	462.6	442.9
25°	710.5	670.6	649.5	628.9	590.4	555.2	523.6	495.6	469.5	446.6	426.9
27.5°	703.1	661.4	639.5	620.7	580.8	542.8	510.3	479.6	454.4	431.5	409.1
30°	694.0	648.2	626.2	603.7	565.3	529.1	493.8	465.4	438.8	412.7	392.6
32.5°	682.5	634.0	609.7	586.8	546.0	508.5	475.9	448.0	422.8	395.8	373.3
35°	666.0	612.9	585.9	565.7	526.3	487.4	456.2	428.7	404.5	376.5	352.3
37.5°	645.0	593.7	566.2	541.4	500.7	464.9	435.6	409.1	385.2	359.6	332.6
40°	620.2	566.6	542.8	516.7	473.6	439.7	412.3	388.4	364.6	340.3	314.2
42.5°	592.3	539.1	512.6	487.4	446.2	412.7	387.1	365.5	343.5	321.1	293.2
45°	558.8	508.9	483.3	459.4	419.6	385.2	361.9	341.3	322.5	299.6	274.8
47.5°	521.3	477.8	451.7	426.0	387.1	357.3	334.4	317.0	300.9	278.0	255.6
50°	484.6	441.6	420.5	394.4	358.7	330.7	307.4	292.7	280.3	257.9	237.7
52.5°	438.4	405.8	385.7	363.2	328.9	300.5	282.2	269.3	254.7	237.3	219.4
55°	397.6	367.4	351.3	330.3	296.4	271.2	255.6	243.7	232.2	216.7	202.5
57.5°	351.3	332.6	316.5	298.2	264.8	243.2	229.5	219.4	208.9	196.1	184.6
60°	302.8	294.1	278.5	263.8	235.4	216.7	205.2	196.1	186.0	175.4	165.8
62.5°	259.7	254.7	245.5	234.1	207.5	191.5	180.0	173.1	165.8	156.2	147.0
65°	219.0	216.7	208.0	199.7	181.4	167.2	157.1	153.0	144.7	137.4	129.2
67.5°	182.8	180.0	175.0	171.3	155.7	142.5	137.4	131.9	125.1	119.6	112.7
70°	146.1	145.7	142.5	137.9	129.6	120.0	115.0	111.3	104.4	100.3	95.3
72.5°	113.6	115.9	113.1	111.3	105.8	98.9	94.4	92.1	86.6	83.4	79.7
75°	84.7	86.6	87.9	84.7	83.4	80.2	76.0	73.7	71.0	66.4	65.0
77.5°	57.7	61.8	61.8	62.8	63.2	61.4	58.2	56.3	53.1	52.2	50.4
80°	38.0	41.7	42.1	43.1	44.4	44.4	42.1	41.7	38.5	38.0	36.6
82.5°	22.0	25.2	27.0	28.4	27.9	29.8	27.9	27.5	25.7	25.7	24.7
85°	11.9	12.4	13.3	14.2	15.1	16.0	16.0	15.6	15.1	14.7	13.7
87.5°	4.6	4.6	5.0	4.6	5.0	6.0	6.4	6.4	6.0	5.5	4.6
90°	16.4	14.7	13.8	12.6	10.2	7.7	5.3	2.9	5.3	7.7	10.2
92.5°	15.4	13.7	12.8	13.0	13.4	13.9	14.3	14.7	14.3	13.9	13.4
95°	20.9	20.7	20.6	24.3	31.7	39.2	46.6	54.0	46.6	39.2	31.7
97.5°	90.4	113.3	124.8	122.4	117.6	112.8	108.0	103.2	108.0	112.8	117.6
100°	133.6	163.7	178.8	176.8	172.9	169.0	165.1	161.2	165.1	169.0	172.9
102.5°	241.7	239.1	237.8	236.5	233.9	231.2	228.6	226.0	228.6	231.2	233.9
105°	303.3	302.2	301.7	301.0	299.7	298.4	297.1	295.8	297.1	298.4	299.7
107.5°	364.9	363.4	362.6	362.3	361.6	360.9	360.3	359.6	360.3	360.9	361.6
110°	429.4	428.1	427.4	427.1	426.4	425.8	425.1	424.5	425.1	425.8	426.4

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	493.9	493.5	493.3	492.6	491.3	490.0	488.7	487.4	488.7	490.0	491.3
115°	554.9	555.1	555.2	554.9	554.2	553.5	552.9	552.2	552.9	553.5	554.2
117.5°	615.1	614.4	614.1	613.7	612.8	611.9	611.1	610.2	611.1	611.9	612.8
120°	672.8	673.0	673.1	672.7	671.8	670.9	670.1	669.2	670.1	670.9	671.8
122.5°	726.8	726.4	726.2	726.0	725.5	725.1	724.6	724.2	724.6	725.1	725.5
125°	779.5	780.0	780.2	779.8	778.9	778.0	777.2	776.3	777.2	778.0	778.9
127.5°	829.0	827.9	827.4	827.3	827.1	826.8	826.6	826.4	826.6	826.8	827.1
130°	876.5	875.8	875.5	875.4	875.2	874.9	874.7	874.5	874.7	874.9	875.2
132.5°	922.0	921.1	920.7	920.5	920.1	919.6	919.2	918.8	919.2	919.6	920.1
135°	963.3	962.4	962.0	962.1	962.3	962.6	962.8	963.0	962.8	962.6	962.3
137.5°	1003.9	1002.8	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3	1002.3
140°	1043.2	1042.8	1042.6	1042.4	1041.9	1041.5	1041.0	1040.6	1041.0	1041.5	1041.9
142.5°	1079.2	1079.0	1078.9	1078.5	1077.6	1076.7	1075.9	1075.0	1075.9	1076.7	1077.6
145°	1113.3	1113.3	1113.3	1113.0	1112.3	1111.7	1111.0	1110.4	1111.0	1111.7	1112.3
147.5°	1143.5	1143.7	1143.8	1143.1	1141.8	1140.5	1139.2	1137.9	1139.2	1140.5	1141.8
150°	1172.0	1172.2	1172.3	1171.9	1171.0	1170.1	1169.2	1168.3	1169.2	1170.1	1171.0
152.5°	1196.2	1196.6	1196.8	1196.5	1195.8	1195.2	1194.5	1193.9	1194.5	1195.2	1195.8
155°	1217.5	1218.2	1218.5	1218.4	1218.2	1217.9	1217.7	1217.5	1217.7	1217.9	1218.2
157.5°	1236.8	1237.7	1238.1	1238.1	1238.1	1238.1	1238.1	1238.1	1238.1	1238.1	1238.1
160°	1252.6	1252.8	1252.9	1253.2	1253.9	1254.5	1255.2	1255.8	1255.2	1254.5	1253.9
162.5°	1267.3	1267.5	1267.6	1268.0	1268.9	1269.8	1270.6	1271.5	1270.6	1269.8	1268.9
165°	1279.4	1279.4	1279.4	1279.9	1281.0	1282.1	1283.2	1284.3	1283.2	1282.1	1281.0
167.5°	1289.9	1290.1	1290.2	1290.7	1291.8	1292.9	1294.0	1295.1	1294.0	1292.9	1291.8
170°	1298.4	1298.2	1298.1	1298.7	1300.0	1301.3	1302.6	1303.9	1302.6	1301.3	1300.0
172.5°	1304.2	1304.0	1303.9	1304.6	1305.9	1307.2	1308.5	1309.8	1308.5	1307.2	1305.9
175°	1308.2	1308.0	1307.9	1308.6	1309.9	1311.2	1312.5	1313.8	1312.5	1311.2	1309.9
177.5°	1310.5	1310.0	1309.8	1310.6	1312.1	1313.6	1315.2	1316.7	1315.2	1313.6	1312.1
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	559.3	558.4	557.5	553.8	550.6	545.1	540.5	538.7	538.2	538.7	537.3
5°	543.3	542.8	539.6	533.2	527.2	520.8	516.2	511.7	508.9	508.9	505.7
7.5°	528.2	524.9	522.2	514.0	507.1	498.4	491.5	487.4	485.1	480.1	480.1
10°	512.1	507.5	503.9	496.1	486.0	477.3	468.6	463.6	459.4	455.8	454.4
12.5°	496.1	492.4	485.5	477.3	467.2	456.2	447.1	443.4	433.8	426.0	426.5
15°	481.0	472.7	469.5	457.6	445.7	435.2	421.9	411.3	403.6	398.5	392.1
17.5°	464.0	455.8	449.8	439.7	424.2	407.7	394.9	380.7	372.9	364.2	360.0
20°	445.2	438.4	433.8	417.8	399.0	379.3	365.1	356.4	347.7	341.3	337.6
22.5°	429.2	420.5	415.0	393.5	372.9	353.2	342.2	334.8	327.5	322.0	320.2
25°	408.6	403.6	390.3	371.5	346.3	333.0	323.4	313.8	309.7	306.0	301.9
27.5°	391.6	379.3	370.1	345.4	329.8	314.7	305.1	297.7	292.7	289.0	285.8
30°	370.6	359.1	346.3	325.7	311.5	297.3	288.6	282.6	277.1	274.8	272.1
32.5°	348.6	338.1	325.7	309.2	291.8	280.8	273.9	267.5	263.8	261.6	258.3
35°	328.9	315.6	307.4	291.8	277.6	265.2	258.8	253.3	249.2	248.3	247.8
37.5°	307.8	297.7	290.0	273.9	262.0	251.5	245.5	239.6	237.3	236.8	235.0
40°	289.5	280.8	273.5	258.3	245.5	235.9	231.3	227.7	225.4	225.4	224.9
42.5°	273.5	264.3	257.0	243.2	231.8	223.1	218.0	214.4	213.5	213.9	213.5
45°	255.6	247.8	240.5	226.3	216.7	210.3	204.8	202.9	201.5	202.0	202.5
47.5°	238.7	232.2	224.9	213.5	202.5	195.6	192.4	190.6	190.6	190.6	191.5
50°	223.5	216.2	209.8	197.9	187.8	182.3	179.6	177.3	177.7	178.2	178.6
52.5°	205.7	199.3	194.7	182.8	175.4	168.6	165.4	165.8	165.4	165.4	166.3
55°	190.1	183.7	179.1	168.1	160.8	156.2	153.5	152.1	152.5	151.6	153.5
57.5°	172.7	167.2	164.0	153.5	147.0	142.9	140.6	138.3	139.3	138.8	138.3
60°	157.6	151.2	146.1	138.8	133.3	128.3	126.9	124.6	125.5	124.6	124.1
62.5°	140.2	135.1	131.5	124.1	119.6	115.4	112.2	110.9	110.4	109.0	107.6
65°	122.8	120.0	116.3	109.0	104.4	101.2	99.4	98.0	97.6	93.9	89.8
67.5°	106.7	104.9	101.2	95.7	91.6	88.4	85.7	83.4	80.6	77.9	75.6
70°	91.6	88.9	86.6	81.5	77.9	74.7	71.9	69.2	67.8	65.0	64.1
72.5°	77.0	74.2	71.9	67.3	64.1	60.9	60.0	56.8	55.4	55.0	55.0
75°	61.8	59.5	58.2	54.1	51.3	49.0	47.6	46.7	45.8	44.9	43.5
77.5°	47.2	45.8	44.9	42.1	39.9	38.5	38.0	34.8	33.9	33.0	32.1
80°	34.4	33.9	33.0	30.7	29.8	26.6	26.6	25.7	25.2	25.2	25.2
82.5°	23.4	22.4	22.0	19.7	19.2	18.8	18.3	17.9	18.3	17.9	18.3
85°	12.4	11.9	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.0	11.5
87.5°	4.6	4.6	4.6	4.6	4.1	4.6	4.6	4.1	4.6	4.6	4.6
90°	12.6	13.8	14.7	16.4	18.1	19.9	21.6	22.9	24.2	25.5	26.8
92.5°	13.0	12.8	13.7	15.4	17.1	18.9	20.6	21.9	23.2	24.5	25.8
95°	24.3	20.6	20.7	20.9	21.2	21.4	21.6	22.9	24.2	25.5	26.8
97.5°	122.4	124.8	113.3	90.4	67.5	44.5	21.6	22.7	23.8	24.9	26.0
100°	176.8	178.8	163.7	133.6	103.5	73.3	43.2	39.5	35.8	32.1	28.4
102.5°	236.5	237.8	239.1	241.7	244.4	247.0	249.6	200.5	151.3	102.2	53.1
105°	301.0	301.7	302.2	303.3	304.4	305.5	306.6	308.6	310.5	312.5	314.4
107.5°	362.3	362.6	363.4	364.9	366.4	368.0	369.5	370.6	371.7	372.8	373.9
110°	427.1	427.4	428.1	429.4	430.7	432.0	433.3	433.7	434.2	434.6	435.1

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	492.6	493.3	493.5	493.9	494.4	494.8	495.2	495.0	494.8	494.6	494.4
115°	554.9	555.2	555.1	554.9	554.6	554.4	554.2	554.6	555.1	555.5	556.0
117.5°	613.7	614.1	614.4	615.1	615.8	616.4	617.1	616.9	616.7	616.4	616.2
120°	672.7	673.1	673.0	672.8	672.5	672.3	672.1	672.5	673.0	673.4	673.9
122.5°	726.0	726.2	726.4	726.8	727.3	727.7	728.1	728.3	728.5	728.8	729.0
125°	779.8	780.2	780.0	779.5	779.1	778.6	778.2	778.9	779.5	780.2	780.9
127.5°	827.3	827.4	827.9	829.0	830.1	831.2	832.3	832.1	831.9	831.6	831.4
130°	875.4	875.5	875.8	876.5	877.2	877.8	878.5	878.7	878.9	879.2	879.4
132.5°	920.5	920.7	921.1	922.0	922.9	923.8	924.7	924.9	925.1	925.3	925.5
135°	962.1	962.0	962.4	963.3	964.2	965.0	965.9	966.3	966.8	967.2	967.7
137.5°	1002.3	1002.3	1002.8	1003.9	1005.0	1006.1	1007.2	1007.6	1008.1	1008.5	1009.0
140°	1042.4	1042.6	1042.8	1043.2	1043.7	1044.1	1044.5	1045.2	1045.8	1046.5	1047.2
142.5°	1078.5	1078.9	1079.0	1079.2	1079.5	1079.7	1079.9	1080.3	1080.8	1081.2	1081.7
145°	1113.0	1113.3	1113.3	1113.3	1113.3	1113.3	1113.3	1113.5	1113.7	1114.0	1114.2
147.5°	1143.1	1143.8	1143.7	1143.5	1143.2	1143.0	1142.8	1143.0	1143.2	1143.5	1143.7
150°	1171.9	1172.3	1172.2	1172.0	1171.7	1171.5	1171.3	1171.3	1171.3	1171.3	1171.3
152.5°	1196.5	1196.8	1196.6	1196.2	1195.7	1195.3	1194.9	1195.3	1195.7	1196.2	1196.6
155°	1218.4	1218.5	1218.2	1217.5	1216.8	1216.2	1215.5	1216.4	1217.2	1218.1	1219.0
157.5°	1238.1	1238.1	1237.7	1236.8	1235.9	1235.1	1234.2	1235.3	1236.4	1237.5	1238.6
160°	1253.2	1252.9	1252.8	1252.6	1252.3	1252.1	1251.9	1253.2	1254.5	1255.8	1257.1
162.5°	1268.0	1267.6	1267.5	1267.3	1267.0	1266.8	1266.6	1267.9	1269.2	1270.5	1271.8
165°	1279.9	1279.4	1279.4	1279.4	1279.4	1279.4	1279.4	1281.1	1282.9	1284.6	1286.3
167.5°	1290.7	1290.2	1290.1	1289.9	1289.6	1289.4	1289.2	1291.2	1293.2	1295.1	1297.1
170°	1298.7	1298.1	1298.2	1298.4	1298.6	1298.8	1299.0	1300.8	1302.5	1304.3	1306.0
172.5°	1304.6	1303.9	1304.0	1304.2	1304.5	1304.7	1304.9	1306.7	1308.4	1310.2	1311.9
175°	1308.6	1307.9	1308.0	1308.2	1308.5	1308.7	1308.9	1310.9	1312.8	1314.8	1316.7
177.5°	1310.6	1309.8	1310.0	1310.5	1310.9	1311.4	1311.8	1313.6	1315.3	1317.1	1318.8
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	537.3	539.1	536.9	538.2	535.0	534.6	535.0	535.0	535.5	535.9	536.4
5°	507.1	506.6	503.9	502.0	500.7	502.0	503.0	503.9	503.0	503.9	504.3
7.5°	478.7	477.3	475.9	472.7	473.6	472.7	475.5	474.1	474.1	476.4	478.2
10°	453.5	450.7	449.8	446.2	443.4	442.9	446.2	447.5	448.9	449.8	453.5
12.5°	421.0	416.8	413.6	415.0	407.2	410.4	411.3	409.5	415.0	421.4	417.8
15°	386.1	386.6	380.2	377.9	371.5	373.3	373.8	378.4	382.9	382.5	388.0
17.5°	360.5	357.7	352.3	351.8	349.0	350.4	350.0	353.6	352.3	354.5	359.1
20°	336.7	334.8	330.3	328.4	329.3	328.4	328.9	329.3	330.7	335.8	334.8
22.5°	317.9	315.6	315.6	313.3	310.6	309.7	311.9	313.3	315.1	316.1	318.4
25°	301.4	299.6	297.3	295.9	293.6	294.1	295.5	297.3	298.7	300.5	302.3
27.5°	284.5	284.5	282.2	281.7	280.8	280.3	282.2	283.1	283.1	284.5	286.3
30°	271.2	271.2	268.9	268.4	268.0	268.0	269.3	269.8	270.3	271.6	272.5
32.5°	258.3	257.9	257.0	257.4	257.0	257.4	257.4	257.9	258.8	259.3	261.1
35°	246.4	246.9	246.0	246.0	245.5	246.0	246.9	247.4	247.8	248.7	248.7
37.5°	235.0	235.9	235.4	236.8	236.8	236.8	236.8	237.7	237.7	237.7	237.3
40°	224.9	224.9	224.5	225.4	226.3	226.3	226.7	226.7	227.2	227.2	226.7
42.5°	213.5	214.4	215.7	216.2	217.1	216.7	218.0	217.6	218.0	217.1	216.2
45°	202.9	202.9	204.8	206.6	207.0	207.0	207.0	208.0	207.0	205.7	205.2
47.5°	191.5	192.4	193.3	195.6	196.1	196.1	196.1	196.1	195.1	195.1	195.1
50°	180.0	180.5	180.9	181.9	183.2	182.8	182.8	182.8	184.6	182.8	183.2
52.5°	166.3	166.7	167.2	169.0	168.6	168.6	169.0	169.0	170.4	169.9	169.0
55°	152.5	152.5	153.5	153.5	153.5	154.4	154.8	155.7	155.3	155.7	156.2
57.5°	138.8	137.9	137.4	137.4	138.8	138.3	138.8	138.8	140.6	141.5	142.0
60°	122.8	122.8	122.3	119.6	119.6	119.1	120.5	121.4	122.3	126.4	126.0
62.5°	106.3	104.4	102.6	103.1	100.3	101.7	100.8	101.7	104.4	107.6	108.1
65°	89.8	88.4	86.6	86.1	85.2	86.6	86.1	86.6	87.9	89.8	92.1
67.5°	75.1	74.7	73.7	73.3	73.3	73.3	74.2	74.2	74.7	76.0	77.4
70°	64.1	63.7	64.1	63.2	63.7	63.2	63.7	64.1	64.6	65.0	66.4
72.5°	54.1	54.1	54.1	53.1	54.1	53.6	53.6	54.1	54.5	55.0	55.9
75°	43.1	42.1	41.2	40.3	39.9	40.8	41.2	40.8	42.1	44.0	44.0
77.5°	32.5	32.1	32.1	32.1	32.5	32.1	33.0	32.5	33.0	33.0	33.9
80°	25.2	24.7	25.2	25.2	24.7	25.7	25.2	25.2	25.7	26.1	25.7
82.5°	18.3	18.8	18.3	18.3	18.3	19.2	18.3	18.3	18.3	18.8	18.8
85°	11.5	11.5	11.5	11.5	11.9	11.5	11.9	11.5	12.4	11.9	11.9
87.5°	4.1	4.6	5.0	5.0	5.0	5.0	4.6	5.0	5.5	5.0	5.5
90°	27.5	27.7	28.2	28.6	29.1	29.5	29.1	28.6	28.2	27.7	27.5
92.5°	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5	26.5
95°	27.5	27.6	27.8	28.1	28.3	28.5	28.3	28.1	27.8	27.6	27.5
97.5°	26.5	26.6	26.8	27.1	27.3	27.5	27.3	27.1	26.8	26.6	26.5
100°	26.5	26.6	26.8	27.1	27.3	27.5	27.3	27.1	26.8	26.6	26.5
102.5°	28.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5
105°	315.4	311.5	303.6	295.7	287.9	280.0	287.9	295.7	303.6	311.5	315.4
107.5°	374.4	374.8	375.7	376.6	377.4	378.3	377.4	376.6	375.7	374.8	374.4
110°	435.3	435.6	436.3	437.0	437.6	438.3	437.6	437.0	436.3	435.6	435.3



TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	494.3	494.7	495.6	496.5	497.3	498.2	497.3	496.5	495.6	494.7	494.3
115°	556.2	556.2	556.2	556.2	556.2	556.2	556.2	556.2	556.2	556.2	556.2
117.5°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
120°	674.1	673.9	673.4	673.0	672.5	672.1	672.5	673.0	673.4	673.9	674.1
122.5°	729.1	728.9	728.4	728.0	727.5	727.1	727.5	728.0	728.4	728.9	729.1
125°	781.2	781.3	781.5	781.8	782.0	782.2	782.0	781.8	781.5	781.3	781.2
127.5°	831.3	831.2	831.0	830.7	830.5	830.3	830.5	830.7	831.0	831.2	831.3
130°	879.5	879.5	879.5	879.5	879.5	879.5	879.5	879.5	879.5	879.5	879.5
132.5°	925.6	925.5	925.3	925.1	924.9	924.7	924.9	925.1	925.3	925.5	925.6
135°	967.9	968.1	968.6	969.0	969.5	969.9	969.5	969.0	968.6	968.1	967.9
137.5°	1009.2	1009.1	1008.9	1008.6	1008.4	1008.2	1008.4	1008.6	1008.9	1009.1	1009.2
140°	1047.5	1047.6	1047.8	1048.1	1048.3	1048.5	1048.3	1048.1	1047.8	1047.6	1047.5
142.5°	1081.9	1081.9	1081.9	1081.9	1081.9	1081.9	1081.9	1081.9	1081.9	1081.9	1081.9
145°	1114.3	1114.5	1115.0	1115.4	1115.9	1116.3	1115.9	1115.4	1115.0	1114.5	1114.3
147.5°	1143.8	1143.9	1144.1	1144.4	1144.6	1144.8	1144.6	1144.4	1144.1	1143.9	1143.8
150°	1171.3	1171.4	1171.6	1171.9	1172.1	1172.3	1172.1	1171.9	1171.6	1171.4	1171.3
152.5°	1196.8	1196.7	1196.5	1196.3	1196.1	1195.9	1196.1	1196.3	1196.5	1196.7	1196.8
155°	1219.4	1219.1	1218.4	1217.8	1217.1	1216.5	1217.1	1217.8	1218.4	1219.1	1219.4
157.5°	1239.1	1238.6	1237.5	1236.4	1235.3	1234.2	1235.3	1236.4	1237.5	1238.6	1239.1
160°	1257.8	1257.1	1255.8	1254.5	1253.2	1251.9	1253.2	1254.5	1255.8	1257.1	1257.8
162.5°	1272.5	1271.7	1270.2	1268.7	1267.1	1265.6	1267.1	1268.7	1270.2	1271.7	1272.5
165°	1287.2	1286.2	1284.3	1282.3	1280.4	1278.4	1280.4	1282.3	1284.3	1286.2	1287.2
167.5°	1298.1	1297.0	1294.8	1292.6	1290.4	1288.2	1290.4	1292.6	1294.8	1297.0	1298.1
170°	1306.9	1305.8	1303.6	1301.5	1299.3	1297.1	1299.3	1301.5	1303.6	1305.8	1306.9
172.5°	1312.8	1311.6	1309.2	1306.8	1304.4	1302.0	1304.4	1306.8	1309.2	1311.6	1312.8
175°	1317.7	1316.4	1313.8	1311.1	1308.5	1305.9	1308.5	1311.1	1313.8	1316.4	1317.7
177.5°	1319.7	1318.4	1315.8	1313.1	1310.5	1307.9	1310.5	1313.1	1315.8	1318.4	1319.7
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5	568.5
2.5°	538.2	540.5	539.6	536.4	537.8	540.5	543.3	546.9	549.2	551.1	552.0
5°	506.6	510.7	509.8	509.8	511.7	516.2	520.8	528.6	531.4	534.6	539.1
7.5°	478.7	481.9	484.6	485.5	488.3	494.3	500.2	508.9	515.8	519.4	522.2
10°	453.9	456.2	460.4	462.6	465.4	472.7	481.4	490.6	497.5	503.9	507.5
12.5°	422.3	431.5	437.0	440.7	444.3	455.3	462.2	472.3	480.5	486.5	492.0
15°	387.1	398.1	401.3	415.5	424.6	433.3	443.9	455.8	463.6	470.4	477.8
17.5°	357.3	365.1	368.7	383.9	391.6	405.4	420.5	435.6	447.5	452.6	459.9
20°	338.5	342.6	350.0	355.0	363.2	379.3	395.8	414.1	432.0	437.0	444.3
22.5°	319.3	324.8	329.8	336.7	343.1	354.1	370.6	390.7	410.0	419.1	427.8
25°	301.9	307.4	310.6	317.9	323.9	334.8	346.3	366.9	389.8	397.6	411.3
27.5°	288.1	291.3	296.8	300.0	306.9	317.0	327.5	343.1	365.5	378.8	392.1
30°	274.4	276.7	281.3	285.8	290.9	297.7	309.7	324.8	345.4	356.8	370.1
32.5°	260.6	264.3	267.1	270.3	275.8	284.0	292.2	306.9	323.4	336.2	349.5
35°	249.2	250.6	254.2	257.9	261.6	268.9	277.6	291.8	306.4	316.5	328.4
37.5°	236.8	239.1	241.9	243.2	249.2	253.8	262.9	273.9	291.3	297.7	309.7
40°	227.2	226.7	229.5	231.8	234.5	241.9	247.4	259.3	273.0	283.1	290.4
42.5°	215.3	215.3	216.2	219.0	222.6	227.2	233.6	243.7	257.9	265.2	273.9
45°	205.7	204.3	204.8	206.6	208.9	213.5	219.9	228.6	242.8	248.7	257.9
47.5°	194.2	192.8	192.8	194.7	196.5	199.7	204.8	214.8	226.3	234.1	240.9
50°	181.4	181.9	181.4	182.8	183.7	186.9	192.4	200.6	211.2	217.6	225.4
52.5°	169.5	168.6	168.1	169.0	170.9	173.1	179.1	186.4	196.5	202.9	209.8
55°	154.8	155.7	155.7	155.7	158.5	159.4	164.0	171.3	181.4	186.4	192.8
57.5°	141.5	141.1	142.0	141.5	143.8	147.0	150.7	156.2	166.3	171.3	177.3
60°	126.9	127.3	127.8	127.8	129.6	132.8	137.0	142.0	150.2	155.3	160.8
62.5°	109.0	111.3	113.6	114.5	117.3	119.6	122.3	127.8	135.1	138.8	143.8
65°	92.1	95.3	98.5	100.8	102.6	104.9	108.6	113.6	119.6	123.2	128.3
67.5°	77.4	79.7	83.8	86.1	89.8	92.5	94.8	98.9	106.3	107.6	111.8
70°	66.9	67.8	69.6	71.5	75.6	77.9	80.6	84.7	90.2	93.4	95.7
72.5°	56.3	56.8	57.7	59.5	61.4	64.1	67.3	71.0	76.0	77.4	80.6
75°	44.9	47.6	47.6	49.0	50.4	51.8	54.5	58.2	61.4	63.7	65.5
77.5°	33.4	34.8	35.7	38.0	39.9	41.2	43.1	45.8	47.6	49.5	50.8
80°	26.1	26.6	27.0	27.0	27.9	29.8	31.6	33.4	35.7	36.6	38.0
82.5°	19.2	19.2	19.2	20.2	20.6	21.1	21.1	22.0	24.3	25.2	26.6
85°	12.4	12.4	12.4	12.4	12.8	13.3	13.7	14.2	14.2	14.2	15.1
87.5°	5.0	6.0	5.5	6.0	6.0	6.0	6.0	6.4	6.4	6.9	6.9
90°	26.8	25.5	24.2	22.9	21.6	19.9	18.1	16.4	14.7	13.8	12.6
92.5°	25.8	24.5	23.2	21.9	20.6	18.9	17.1	15.4	13.7	12.8	13.0
95°	26.8	25.5	24.2	22.9	21.6	21.4	21.2	20.9	20.7	20.6	24.3
97.5°	26.0	24.9	23.8	22.7	21.6	44.5	67.5	90.4	113.3	124.8	122.4
100°	28.4	32.1	35.8	39.5	43.2	73.3	103.5	133.6	163.7	178.8	176.8
102.5°	53.1	102.2	151.3	200.5	249.6	247.0	244.4	241.7	239.1	237.8	236.5
105°	314.4	312.5	310.5	308.6	306.6	305.5	304.4	303.3	302.2	301.7	301.0
107.5°	373.9	372.8	371.7	370.6	369.5	368.0	366.4	364.9	363.4	362.6	362.3
110°	435.1	434.6	434.2	433.7	433.3	432.0	430.7	429.4	428.1	427.4	427.1

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	494.4	494.6	494.8	495.0	495.2	494.8	494.4	493.9	493.5	493.3	492.6
115°	556.0	555.5	555.1	554.6	554.2	554.4	554.6	554.9	555.1	555.2	554.9
117.5°	616.2	616.4	616.7	616.9	617.1	616.4	615.8	615.1	614.4	614.1	613.7
120°	673.9	673.4	673.0	672.5	672.1	672.3	672.5	672.8	673.0	673.1	672.7
122.5°	729.0	728.8	728.5	728.3	728.1	727.7	727.3	726.8	726.4	726.2	726.0
125°	780.9	780.2	779.5	778.9	778.2	778.6	779.1	779.5	780.0	780.2	779.8
127.5°	831.4	831.6	831.9	832.1	832.3	831.2	830.1	829.0	827.9	827.4	827.3
130°	879.4	879.2	878.9	878.7	878.5	877.8	877.2	876.5	875.8	875.5	875.4
132.5°	925.5	925.3	925.1	924.9	924.7	923.8	922.9	922.0	921.1	920.7	920.5
135°	967.7	967.2	966.8	966.3	965.9	965.0	964.2	963.3	962.4	962.0	962.1
137.5°	1009.0	1008.5	1008.1	1007.6	1007.2	1006.1	1005.0	1003.9	1002.8	1002.3	1002.3
140°	1047.2	1046.5	1045.8	1045.2	1044.5	1044.1	1043.7	1043.2	1042.8	1042.6	1042.4
142.5°	1081.7	1081.2	1080.8	1080.3	1079.9	1079.7	1079.5	1079.2	1079.0	1078.9	1078.5
145°	1114.2	1114.0	1113.7	1113.5	1113.3	1113.3	1113.3	1113.3	1113.3	1113.3	1113.0
147.5°	1143.7	1143.5	1143.2	1143.0	1142.8	1143.0	1143.2	1143.5	1143.7	1143.8	1143.1
150°	1171.3	1171.3	1171.3	1171.3	1171.3	1171.5	1171.7	1172.0	1172.2	1172.3	1171.9
152.5°	1196.6	1196.2	1195.7	1195.3	1194.9	1195.3	1195.7	1196.2	1196.6	1196.8	1196.5
155°	1219.0	1218.1	1217.2	1216.4	1215.5	1216.2	1216.8	1217.5	1218.2	1218.5	1218.4
157.5°	1238.6	1237.5	1236.4	1235.3	1234.2	1235.1	1235.9	1236.8	1237.7	1238.1	1238.1
160°	1257.1	1255.8	1254.5	1253.2	1251.9	1252.1	1252.3	1252.6	1252.8	1252.9	1253.2
162.5°	1271.8	1270.5	1269.2	1267.9	1266.6	1266.8	1267.0	1267.3	1267.5	1267.6	1268.0
165°	1286.3	1284.6	1282.9	1281.1	1279.4	1279.4	1279.4	1279.4	1279.4	1279.4	1279.9
167.5°	1297.1	1295.1	1293.2	1291.2	1289.2	1289.4	1289.6	1289.9	1290.1	1290.2	1290.7
170°	1306.0	1304.3	1302.5	1300.8	1299.0	1298.8	1298.6	1298.4	1298.2	1298.1	1298.7
172.5°	1311.9	1310.2	1308.4	1306.7	1304.9	1304.7	1304.5	1304.2	1304.0	1303.9	1304.6
175°	1316.7	1314.8	1312.8	1310.9	1308.9	1308.7	1308.5	1308.2	1308.0	1307.9	1308.6
177.5°	1318.8	1317.1	1315.3	1313.6	1311.8	1311.4	1310.9	1310.5	1310.0	1309.8	1310.6
180°	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8	1313.8

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	568.5	568.5	568.5	568.5
2.5°	555.6	558.4	563.0	569.4
5°	542.8	550.6	557.9	567.5
7.5°	531.4	540.5	550.6	564.3
10°	518.1	529.5	542.4	559.3
12.5°	502.5	518.5	533.2	551.5
15°	491.0	503.0	521.7	543.3
17.5°	475.0	491.0	509.8	534.1
20°	459.9	476.8	497.9	523.1
22.5°	443.9	463.1	484.2	511.2
25°	427.4	448.0	469.1	497.9
27.5°	412.3	431.0	454.9	484.2
30°	393.9	415.5	438.4	469.1
32.5°	376.1	398.5	421.9	452.6
35°	356.8	379.3	404.9	434.2
37.5°	338.1	362.8	386.1	414.5
40°	317.4	343.1	367.4	396.2
42.5°	297.3	323.9	348.1	372.9
45°	278.5	304.6	326.6	350.0
47.5°	260.6	284.0	306.4	327.5
50°	243.2	262.9	283.5	300.9
52.5°	224.9	243.7	260.2	275.8
55°	208.4	223.1	237.7	251.9
57.5°	188.7	203.4	216.2	227.2
60°	172.2	181.4	193.8	205.2
62.5°	153.5	164.0	173.6	180.9
65°	135.1	144.3	151.6	158.0
67.5°	119.6	125.1	130.5	137.4
70°	100.8	105.4	111.8	116.8
72.5°	84.7	88.4	91.6	97.6
75°	68.7	71.9	73.7	79.2
77.5°	53.1	56.3	57.7	60.9
80°	40.8	41.2	43.1	45.8
82.5°	27.9	28.9	29.3	31.6
85°	16.0	18.3	17.9	18.8
87.5°	6.9	7.3	8.2	9.2
90°	10.2	7.7	5.3	2.9
92.5°	13.4	13.9	14.3	14.7
95°	31.7	39.2	46.6	54.0
97.5°	117.6	112.8	108.0	103.2
100°	172.9	169.0	165.1	161.2
102.5°	233.9	231.2	228.6	226.0
105°	299.7	298.4	297.1	295.8
107.5°	361.6	360.9	360.3	359.6
110°	426.4	425.8	425.1	424.5

TEST NUMBER: P1013303

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	491.3	490.0	488.7	487.4
115°	554.2	553.5	552.9	552.2
117.5°	612.8	611.9	611.1	610.2
120°	671.8	670.9	670.1	669.2
122.5°	725.5	725.1	724.6	724.2
125°	778.9	778.0	777.2	776.3
127.5°	827.1	826.8	826.6	826.4
130°	875.2	874.9	874.7	874.5
132.5°	920.1	919.6	919.2	918.8
135°	962.3	962.6	962.8	963.0
137.5°	1002.3	1002.3	1002.3	1002.3
140°	1041.9	1041.5	1041.0	1040.6
142.5°	1077.6	1076.7	1075.9	1075.0
145°	1112.3	1111.7	1111.0	1110.4
147.5°	1141.8	1140.5	1139.2	1137.9
150°	1171.0	1170.1	1169.2	1168.3
152.5°	1195.8	1195.2	1194.5	1193.9
155°	1218.2	1217.9	1217.7	1217.5
157.5°	1238.1	1238.1	1238.1	1238.1
160°	1253.9	1254.5	1255.2	1255.8
162.5°	1268.9	1269.8	1270.6	1271.5
165°	1281.0	1282.1	1283.2	1284.3
167.5°	1291.8	1292.9	1294.0	1295.1
170°	1300.0	1301.3	1302.6	1303.9
172.5°	1305.9	1307.2	1308.5	1309.8
175°	1309.9	1311.2	1312.5	1313.8
177.5°	1312.1	1313.6	1315.2	1316.7
180°	1313.8	1313.8	1313.8	1313.8

(END OF REPORT)