

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013310

Luminaire Tested: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013310
REPORT IS A COMBINATION OF REPORTS P999265 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6199.0 lumens
Efficiency: N/A
Efficacy: 129.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31
1	92	88	84	81	82	78	75	73	60	58	56	43	42	41	28	27	27
2	84	77	71	66	74	69	64	60	53	50	47	38	36	35	25	24	23
3	77	68	61	55	68	60	55	50	47	43	40	34	32	29	22	21	20
4	70	60	53	47	62	54	47	42	42	37	34	30	28	25	20	18	17
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	16	15
6	59	48	40	35	52	43	36	31	33	29	25	25	22	19	16	15	13
7	55	43	35	30	48	39	32	27	30	26	22	22	19	17	15	13	12
8	50	39	31	26	45	35	29	24	27	23	20	20	17	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4623	4623	4623	4623
5°	4623	5223	4630	3992
10°	4598	6021	4594	3472
15°	4544	6777	4544	2907
20°	4486	7348	4462	2560
25°	4416	7379	4395	2312
30°	4342	6274	4308	2141
35°	4236	4734	4183	2014
40°	4119	3431	4039	1915
45°	3927	2607	3829	1828
50°	3697	2107	3596	1699
55°	3448	1745	3336	1527
60°	3198	1476	3056	1271
65°	2886	1202	2795	1009
70°	2599	974	2476	820
75°	2277	702	2118	602
80°	1880	466	1711	442
85°	1361	239	1128	239

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 5787 cd/sqm

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.9	0.9
10°-20°	165.8	2.7
20°-30°	259.7	4.2
30°-40°	288.3	4.7
40°-50°	255.5	4.1
50°-60°	199.1	3.2
60°-70°	130.2	2.1
70°-80°	63.9	1.0
80°-90°	18.7	0.3
90°-100°	51.1	0.8
100°-110°	336.5	5.4
110°-120°	642.5	10.4
120°-130°	815.7	13.2
130°-140°	872.6	14.1
140°-150°	815.9	13.2
150°-160°	658.0	10.6
160°-170°	424.3	6.8
170°-180°	146.2	2.4
0°-30°	480.3	7.7
0°-40°	768.6	12.4
0°-60°	1223.3	19.7
0°-90°	1436.2	23.2
90°-120°	1030.1	16.6
90°-150°	3534.2	57.0
90°-180°	4763.0	76.8
0°-180°	6199.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	567	567	567	567	567	
5°	566	655	567	501	566	54
15°	542	868	542	372	542	153
25°	496	936	494	293	496	229
35°	433	576	428	245	433	271
45°	349	295	340	206	349	269
55°	251	176	243	154	251	225
65°	158	103	153	86	158	157
75°	79	48	74	41	79	84
85°	19	11	16	11	19	21
90°	4	34	4	34	4	5
95°	63	33	63	33	63	78
105°	346	328	346	328	346	363
115°	647	652	647	652	647	637
125°	910	916	910	916	910	812
135°	1128	1136	1128	1136	1128	869
145°	1301	1308	1301	1308	1301	813
155°	1426	1425	1426	1425	1426	658
165°	1505	1498	1505	1498	1505	425
175°	1539	1530	1539	1530	1539	147
180°	1539	1539	1539	1539	1539	

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9
2.5°	567.8	572.8	575.6	577.8	582.4	584.2	587.9	588.8	592.5	592.0	590.6
5°	566.0	574.6	581.0	587.9	596.1	600.7	605.7	613.0	616.7	621.7	624.9
7.5°	562.8	574.6	585.1	595.7	608.9	616.2	622.6	634.0	643.6	651.8	661.0
10°	557.7	572.8	588.3	602.5	620.8	629.5	639.1	656.0	669.2	680.6	695.2
12.5°	550.0	571.0	588.3	607.5	630.8	642.7	655.5	675.6	691.1	709.9	728.1
15°	541.8	565.1	587.9	613.0	639.5	653.2	666.0	693.0	716.7	738.2	758.3
17.5°	532.6	558.2	583.3	611.2	643.2	660.1	675.1	707.6	733.6	761.5	781.6
20°	521.7	549.5	578.3	609.4	645.4	664.2	681.1	718.1	746.9	777.0	802.1
22.5°	509.8	539.9	571.4	605.2	642.7	663.3	682.9	722.6	756.0	783.9	817.7
25°	496.5	528.5	560.9	596.6	638.6	661.0	681.1	720.4	756.0	792.5	825.4
27.5°	482.8	515.7	549.5	587.0	629.9	651.8	674.7	712.6	754.2	793.9	827.2
30°	467.8	499.7	535.4	571.0	616.7	638.6	661.9	703.0	748.2	788.0	824.1
32.5°	451.3	484.2	518.0	555.0	599.8	623.5	645.0	691.6	737.7	777.0	810.8
35°	433.0	464.1	496.1	534.0	578.3	599.8	625.3	673.8	720.4	761.9	783.9
37.5°	413.4	443.1	472.8	510.2	552.7	578.8	603.9	652.8	702.1	730.0	741.4
40°	395.1	421.2	447.2	483.3	526.2	553.2	578.8	629.5	672.9	694.3	685.6
42.5°	371.8	398.8	422.1	455.4	498.8	523.9	550.0	602.5	637.7	646.4	624.9
45°	349.0	371.4	393.8	426.2	471.9	493.3	521.2	570.1	599.3	591.5	560.0
47.5°	326.6	344.9	365.9	397.4	438.5	464.1	490.1	532.6	553.2	542.2	498.4
50°	300.1	318.4	340.3	367.7	407.5	432.1	452.7	492.0	507.5	480.5	427.6
52.5°	275.0	291.0	309.7	335.3	373.2	395.6	418.0	451.8	456.8	425.7	370.0
55°	251.2	264.0	283.7	304.2	338.9	362.7	378.2	407.0	405.6	366.8	318.8
57.5°	226.6	238.4	251.7	273.2	306.0	323.9	340.8	365.9	352.6	319.8	272.2
60°	204.6	211.5	224.7	245.3	273.2	288.7	301.9	315.6	304.2	268.6	232.0
62.5°	180.4	188.2	197.8	214.2	238.9	253.5	263.1	269.0	257.2	229.8	196.4
65°	157.6	164.4	174.5	189.1	207.8	218.8	223.8	227.9	221.5	190.5	164.0
67.5°	137.0	141.6	150.7	160.3	180.4	183.2	190.0	191.9	179.1	155.3	134.3
70°	116.5	121.0	125.2	136.6	145.7	150.7	152.1	152.1	139.3	123.8	106.4
72.5°	97.3	100.0	104.1	111.9	116.9	120.6	122.4	120.1	108.3	95.5	82.7
75°	79.0	80.4	84.0	89.1	93.2	91.8	91.4	88.6	79.9	70.8	63.5
77.5°	60.8	61.7	65.8	67.1	67.1	68.5	66.7	64.0	56.6	49.8	46.6
80°	45.7	47.0	47.5	48.4	47.5	47.5	46.1	41.6	37.9	34.7	32.4
82.5°	31.5	32.4	32.9	31.5	32.4	31.1	28.8	25.6	23.3	22.8	21.9
85°	18.7	19.2	18.7	18.7	17.4	16.9	15.1	14.6	13.7	13.7	13.2
87.5°	9.1	8.7	7.8	6.9	6.9	6.4	6.9	5.9	6.9	6.4	5.9
90°	3.5	6.3	9.1	11.9	14.7	16.1	17.1	19.2	21.2	23.3	25.3
92.5°	17.3	16.8	16.3	15.8	15.3	15.0	16.0	18.1	20.1	22.2	24.2
95°	63.3	54.6	45.9	37.2	28.5	24.2	24.3	24.6	24.8	25.1	25.3
97.5°	120.9	126.5	132.1	137.8	143.4	146.2	132.8	105.9	79.0	52.2	25.3
100°	188.8	193.4	198.0	202.6	207.2	209.5	191.9	156.6	121.3	86.0	50.7
102.5°	264.8	267.9	270.9	274.0	277.1	278.6	280.1	283.2	286.3	289.3	292.4
105°	346.5	348.0	349.6	351.1	352.6	353.4	354.0	355.3	356.6	357.9	359.2
107.5°	421.4	422.2	422.9	423.7	424.4	424.8	425.7	427.5	429.3	431.1	432.9
110°	497.3	498.1	498.9	499.6	500.4	500.8	501.6	503.1	504.6	506.2	507.7

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	571.0	572.5	574.1	575.6	577.1	577.9	578.2	578.7	579.2	579.7	580.2
115°	647.0	647.8	648.5	649.3	650.0	650.4	650.3	650.0	649.8	649.5	649.3
117.5°	714.9	715.9	716.9	718.0	719.0	719.5	719.9	720.7	721.4	722.2	723.0
120°	784.0	785.0	786.0	787.1	788.1	788.6	788.5	788.2	787.9	787.7	787.4
122.5°	848.5	849.0	849.5	850.0	850.5	850.8	851.1	851.6	852.1	852.6	853.1
125°	909.5	910.5	911.5	912.6	913.6	914.1	913.8	913.3	912.8	912.3	911.8
127.5°	968.2	968.4	968.7	968.9	969.2	969.3	969.9	971.2	972.5	973.8	975.1
130°	1024.6	1024.8	1025.1	1025.3	1025.6	1025.7	1026.1	1026.9	1027.6	1028.4	1029.2
132.5°	1076.4	1076.9	1077.4	1077.9	1078.4	1078.7	1079.2	1080.2	1081.3	1082.3	1083.3
135°	1128.2	1128.0	1127.7	1127.5	1127.2	1127.1	1127.6	1128.6	1129.7	1130.7	1131.7
137.5°	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.9	1176.2	1177.5	1178.7	1180.0
140°	1219.2	1219.7	1220.2	1220.7	1221.2	1221.5	1221.8	1222.3	1222.8	1223.3	1223.8
142.5°	1259.4	1260.4	1261.5	1262.5	1263.6	1264.1	1264.2	1264.5	1264.7	1265.0	1265.2
145°	1300.9	1301.7	1302.4	1303.2	1303.9	1304.3	1304.3	1304.3	1304.3	1304.3	1304.3
147.5°	1333.1	1334.6	1336.2	1337.7	1339.2	1340.0	1339.9	1339.6	1339.4	1339.1	1338.9
150°	1368.8	1369.8	1370.8	1371.9	1372.9	1373.4	1373.3	1373.0	1372.8	1372.5	1372.3
152.5°	1398.7	1399.5	1400.3	1401.0	1401.8	1402.2	1401.9	1401.4	1400.9	1400.4	1399.9
155°	1426.4	1426.6	1426.9	1427.1	1427.4	1427.5	1427.1	1426.4	1425.6	1424.9	1424.1
157.5°	1450.6	1450.6	1450.6	1450.6	1450.6	1450.6	1450.1	1449.0	1448.0	1446.9	1445.9
160°	1471.3	1470.5	1469.7	1469.0	1468.2	1467.8	1467.7	1467.4	1467.2	1466.9	1466.7
162.5°	1489.7	1488.7	1487.7	1486.6	1485.6	1485.1	1485.0	1484.7	1484.4	1484.2	1483.9
165°	1504.7	1503.4	1502.1	1500.8	1499.5	1498.9	1498.9	1498.9	1498.9	1498.9	1498.9
167.5°	1517.3	1516.0	1514.8	1513.5	1512.2	1511.6	1511.5	1511.2	1510.9	1510.7	1510.4
170°	1527.7	1526.2	1524.6	1523.1	1521.6	1520.8	1520.9	1521.2	1521.4	1521.7	1521.9
172.5°	1534.6	1533.1	1531.5	1530.0	1528.5	1527.7	1527.8	1528.1	1528.3	1528.6	1528.8
175°	1539.2	1537.7	1536.1	1534.6	1533.1	1532.3	1532.4	1532.7	1532.9	1533.2	1533.4
177.5°	1542.7	1540.9	1539.1	1537.3	1535.5	1534.6	1534.9	1535.4	1535.9	1536.4	1536.9
180°	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9
2.5°	594.3	599.3	599.8	604.3	603.0	600.7	604.8	602.1	607.5	605.7	608.0
5°	629.0	635.9	641.8	645.4	651.8	650.5	657.3	655.0	660.1	655.0	661.4
7.5°	669.7	681.1	687.0	696.6	699.3	699.8	708.0	709.9	713.1	709.9	713.5
10°	709.4	723.1	736.8	744.6	749.6	756.4	763.8	767.0	769.2	766.0	768.3
12.5°	745.5	767.0	782.0	797.6	801.2	807.1	814.9	814.0	823.1	821.3	825.4
15°	778.8	802.6	820.9	833.2	843.2	848.3	862.9	863.8	863.3	867.9	865.2
17.5°	808.5	828.6	854.7	870.6	883.0	883.0	891.2	908.1	906.7	906.3	909.0
20°	832.7	855.6	879.8	906.7	916.8	918.6	930.0	938.7	940.1	940.1	940.1
22.5°	851.0	878.0	904.0	923.2	930.9	937.3	947.4	952.9	954.7	953.8	954.7
25°	860.1	885.7	912.2	929.6	934.1	937.8	938.7	941.9	941.4	936.0	939.2
27.5°	862.0	886.6	904.0	908.6	906.3	904.0	889.4	890.7	886.6	878.4	881.6
30°	853.7	867.0	866.5	852.4	848.3	838.7	825.4	805.8	789.8	782.9	785.2
32.5°	824.1	824.1	807.6	775.6	761.5	744.1	720.4	702.5	681.5	677.0	685.6
35°	782.9	759.6	729.5	687.5	666.0	653.2	612.1	599.3	581.5	576.5	580.6
37.5°	719.0	680.2	636.3	597.0	578.8	555.9	519.8	501.6	488.8	480.1	484.2
40°	647.3	600.2	554.5	506.1	486.0	467.3	440.3	423.9	403.3	404.3	405.6
42.5°	578.8	523.5	472.3	427.6	408.4	392.8	374.1	354.0	346.7	344.4	342.1
45°	506.1	447.2	399.2	365.9	348.5	333.9	316.6	305.1	296.5	294.6	296.9
47.5°	437.6	387.8	342.1	311.1	296.9	289.6	275.9	265.4	259.9	255.3	258.1
50°	375.5	328.9	292.3	266.3	256.3	251.2	238.4	233.0	227.5	226.1	225.7
52.5°	324.3	284.6	253.1	232.0	224.3	221.5	212.0	204.2	199.6	201.0	201.9
55°	277.7	243.9	219.3	202.4	196.0	192.8	185.9	180.4	177.2	175.9	176.8
57.5°	236.6	207.4	189.6	175.9	170.8	169.5	162.2	160.3	158.0	156.7	156.7
60°	199.2	178.6	162.2	154.4	148.9	147.5	142.1	139.8	139.3	138.0	137.0
62.5°	167.6	150.7	139.3	131.1	128.8	128.4	124.7	122.0	120.6	119.7	119.7
65°	140.2	127.9	118.3	112.4	110.5	109.6	105.5	104.6	103.7	102.8	102.3
67.5°	116.9	106.0	99.1	95.0	92.7	93.2	90.9	89.1	89.1	88.6	88.2
70°	94.6	87.7	81.8	79.5	78.6	77.7	76.7	75.4	74.9	74.9	74.9
72.5°	74.5	69.9	66.7	65.3	64.4	63.5	62.6	62.6	62.6	62.1	62.1
75°	57.1	55.3	53.0	51.6	51.6	52.5	51.2	49.8	48.4	47.5	48.0
77.5°	42.9	42.0	40.7	38.4	38.8	37.9	37.9	37.0	37.5	37.5	36.5
80°	31.5	30.1	29.7	28.3	28.8	28.3	27.9	27.9	27.0	27.0	27.0
82.5°	21.9	20.6	20.6	20.1	19.6	19.6	19.2	19.2	19.6	18.7	18.7
85°	13.2	12.8	12.8	11.9	11.9	11.9	11.9	12.3	11.9	11.4	11.4
87.5°	5.9	6.4	5.9	5.5	5.5	5.5	5.0	5.0	4.6	5.0	5.0
90°	26.8	28.4	29.9	31.4	32.2	32.5	33.0	33.5	34.0	34.5	34.0
92.5°	25.7	27.3	28.8	30.3	31.1	31.1	31.1	31.1	31.1	31.1	31.1
95°	26.8	28.4	29.9	31.4	32.2	32.3	32.6	32.9	33.1	33.4	33.1
97.5°	26.6	27.9	29.2	30.5	31.1	31.2	31.5	31.7	32.0	32.2	32.0
100°	46.3	42.0	37.6	33.3	31.1	31.2	31.5	31.7	32.0	32.2	32.0
102.5°	234.8	177.3	119.7	62.2	33.4	33.4	33.4	33.4	33.4	33.4	33.4
105°	361.5	363.8	366.1	368.4	369.5	364.9	355.7	346.5	337.3	328.1	337.3
107.5°	434.2	435.4	436.7	438.0	438.6	439.1	440.1	441.2	442.2	443.2	442.2
110°	508.2	508.7	509.2	509.7	510.0	510.4	511.1	511.9	512.6	513.4	512.6

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	580.0	579.7	579.5	579.2	579.1	579.6	580.6	581.7	582.7	583.7	582.7
115°	649.8	650.3	650.8	651.3	651.6	651.6	651.6	651.6	651.6	651.6	651.6
117.5°	722.7	722.5	722.2	721.9	721.8	721.8	721.8	721.8	721.8	721.8	721.8
120°	787.9	788.4	788.9	789.4	789.7	789.4	788.9	788.4	787.9	787.4	787.9
122.5°	853.3	853.6	853.8	854.1	854.2	853.9	853.4	852.9	852.4	851.9	852.4
125°	912.6	913.3	914.1	914.8	915.2	915.3	915.6	915.9	916.1	916.4	916.1
127.5°	974.8	974.6	974.3	974.0	973.9	973.8	973.5	973.3	973.0	972.8	973.0
130°	1029.5	1029.7	1030.0	1030.3	1030.4	1030.4	1030.4	1030.4	1030.4	1030.4	1030.4
132.5°	1083.6	1083.8	1084.1	1084.4	1084.5	1084.4	1084.1	1083.8	1083.6	1083.3	1083.6
135°	1132.2	1132.7	1133.2	1133.7	1134.0	1134.3	1134.8	1135.3	1135.8	1136.3	1135.8
137.5°	1180.5	1181.0	1181.5	1182.0	1182.3	1182.2	1181.9	1181.7	1181.4	1181.2	1181.4
140°	1224.6	1225.3	1226.1	1226.8	1227.2	1227.3	1227.6	1227.9	1228.1	1228.4	1228.1
142.5°	1265.7	1266.2	1266.7	1267.2	1267.5	1267.5	1267.5	1267.5	1267.5	1267.5	1267.5
145°	1304.6	1304.8	1305.1	1305.4	1305.8	1305.8	1306.3	1306.8	1307.3	1307.8	1307.3
147.5°	1339.1	1339.4	1339.6	1339.9	1340.0	1340.1	1340.4	1340.7	1340.9	1341.2	1340.9
150°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.4	1372.7	1372.9	1373.2	1373.4	1373.2
152.5°	1400.4	1400.9	1401.4	1401.9	1402.2	1402.1	1401.8	1401.6	1401.3	1401.1	1401.3
155°	1425.1	1426.1	1427.2	1428.2	1428.7	1428.3	1427.5	1426.8	1426.0	1425.2	1426.0
157.5°	1447.2	1448.5	1449.8	1451.1	1451.7	1451.1	1449.8	1448.5	1447.2	1445.9	1447.2
160°	1468.2	1469.8	1471.3	1472.8	1473.6	1472.8	1471.3	1469.8	1468.2	1466.7	1468.2
162.5°	1485.4	1487.0	1488.5	1490.0	1490.8	1489.9	1488.1	1486.4	1484.6	1482.8	1484.6
165°	1500.9	1503.0	1505.0	1507.1	1508.1	1507.0	1504.7	1502.4	1500.1	1497.8	1500.1
167.5°	1512.7	1515.0	1517.3	1519.6	1520.8	1519.5	1517.0	1514.4	1511.9	1509.3	1511.9
170°	1523.9	1526.0	1528.0	1530.1	1531.1	1529.8	1527.3	1524.7	1522.2	1519.6	1522.2
172.5°	1530.8	1532.9	1534.9	1537.0	1538.0	1536.6	1533.8	1531.0	1528.2	1525.4	1528.2
175°	1535.7	1538.0	1540.3	1542.6	1543.8	1542.3	1539.2	1536.1	1533.1	1530.0	1533.1
177.5°	1538.9	1541.0	1543.0	1545.1	1546.1	1544.6	1541.5	1538.4	1535.4	1532.3	1535.4
180°	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9
2.5°	609.4	606.2	605.7	605.7	600.7	603.4	597.9	592.0	589.3	589.3	584.2
5°	660.1	656.9	653.7	648.6	648.6	645.9	637.2	628.5	622.1	616.7	610.7
7.5°	712.1	708.9	699.8	694.8	697.5	692.0	680.6	666.0	655.0	646.4	634.0
10°	768.8	760.1	755.5	752.8	743.2	737.3	724.0	702.5	688.8	677.4	661.4
12.5°	814.9	817.7	800.3	801.7	792.1	783.9	763.3	742.7	722.2	706.2	682.4
15°	864.7	856.5	846.0	837.8	834.6	824.5	807.1	779.7	757.4	732.2	705.3
17.5°	904.0	897.6	887.5	879.8	872.9	848.7	834.1	809.9	779.3	754.6	721.7
20°	937.3	931.4	917.2	912.2	899.9	882.5	861.5	824.1	796.6	769.7	737.7
22.5°	951.5	945.6	933.2	926.8	919.1	902.2	882.1	846.4	812.6	778.8	745.0
25°	939.6	939.6	933.7	931.4	924.5	909.5	888.9	858.8	822.7	786.1	745.9
27.5°	882.1	893.5	897.6	899.9	899.9	900.3	886.2	856.9	821.8	786.1	744.1
30°	798.9	818.1	835.0	840.0	848.7	858.3	864.2	850.1	818.6	781.1	739.1
32.5°	694.3	719.0	750.5	758.3	770.1	798.9	814.9	820.9	803.5	770.6	725.8
35°	590.2	621.2	640.4	664.2	675.1	717.6	753.2	774.7	770.6	751.0	710.3
37.5°	499.3	517.1	540.4	565.5	587.4	628.1	672.4	714.0	730.9	721.3	690.7
40°	412.0	433.0	460.9	481.5	496.5	537.2	592.0	637.2	674.2	680.2	661.4
42.5°	350.4	371.4	388.3	410.7	422.5	461.8	510.2	566.9	610.7	634.0	625.8
45°	302.9	315.6	329.3	342.1	356.8	391.5	436.2	498.4	547.7	580.6	583.8
47.5°	261.3	272.7	284.6	296.5	304.7	331.6	372.7	423.4	477.3	522.6	540.4
50°	232.0	237.5	246.2	253.1	262.7	286.0	318.8	362.7	419.8	468.7	492.0
52.5°	203.3	210.1	217.0	222.9	229.3	245.8	275.9	313.8	363.1	413.4	442.2
55°	179.1	184.5	190.9	195.0	198.7	213.3	236.2	265.4	307.9	355.4	391.0
57.5°	159.4	161.7	167.2	169.5	173.6	185.5	201.9	227.9	262.2	308.3	337.6
60°	138.0	142.5	146.6	148.5	151.7	159.9	171.3	195.5	225.2	259.0	292.3
62.5°	120.6	122.4	125.6	127.9	130.2	138.9	148.5	166.7	189.1	217.4	248.0
65°	104.6	105.5	107.3	110.5	111.9	118.3	123.8	137.0	158.0	179.5	210.1
67.5°	88.2	89.1	91.4	93.2	94.6	98.7	104.6	114.2	125.6	149.4	166.3
70°	75.4	75.4	76.7	77.7	79.0	80.9	84.0	91.4	101.9	116.9	132.5
72.5°	63.0	63.0	63.0	64.4	64.4	65.8	67.6	72.6	79.9	91.8	101.9
75°	48.9	49.3	50.2	50.2	50.7	52.5	53.9	55.3	58.9	66.7	75.8
77.5°	37.0	37.9	38.4	37.5	38.4	38.4	40.2	42.0	43.9	46.1	53.0
80°	27.4	27.9	27.0	27.4	27.4	28.3	29.2	28.8	29.7	32.4	34.3
82.5°	18.3	18.7	18.7	18.7	18.7	20.1	20.1	19.6	20.1	20.6	21.0
85°	11.4	11.0	11.0	11.4	11.0	11.0	11.4	11.9	11.4	11.9	12.3
87.5°	5.0	5.0	5.0	5.0	4.6	4.6	5.0	4.6	5.0	4.6	4.1
90°	33.5	33.0	32.5	32.2	31.4	29.9	28.4	26.8	25.3	23.3	21.2
92.5°	31.1	31.1	31.1	31.1	30.3	28.8	27.3	25.7	24.2	22.2	20.1
95°	32.9	32.6	32.3	32.2	31.4	29.9	28.4	26.8	25.3	25.1	24.8
97.5°	31.7	31.5	31.2	31.1	30.5	29.2	27.9	26.6	25.3	52.2	79.0
100°	31.7	31.5	31.2	31.1	33.3	37.6	42.0	46.3	50.7	86.0	121.3
102.5°	33.4	33.4	33.4	33.4	62.2	119.7	177.3	234.8	292.4	289.3	286.3
105°	346.5	355.7	364.9	369.5	368.4	366.1	363.8	361.5	359.2	357.9	356.6
107.5°	441.2	440.1	439.1	438.6	438.0	436.7	435.4	434.2	432.9	431.1	429.3
110°	511.9	511.1	510.4	510.0	509.7	509.2	508.7	508.2	507.7	506.2	504.6

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	581.7	580.6	579.6	579.1	579.2	579.5	579.7	580.0	580.2	579.7	579.2
115°	651.6	651.6	651.6	651.6	651.3	650.8	650.3	649.8	649.3	649.5	649.8
117.5°	721.8	721.8	721.8	721.8	721.9	722.2	722.5	722.7	723.0	722.2	721.4
120°	788.4	788.9	789.4	789.7	789.4	788.9	788.4	787.9	787.4	787.7	787.9
122.5°	852.9	853.4	853.9	854.2	854.1	853.8	853.6	853.3	853.1	852.6	852.1
125°	915.9	915.6	915.3	915.2	914.8	914.1	913.3	912.6	911.8	912.3	912.8
127.5°	973.3	973.5	973.8	973.9	974.0	974.3	974.6	974.8	975.1	973.8	972.5
130°	1030.4	1030.4	1030.4	1030.4	1030.3	1030.0	1029.7	1029.5	1029.2	1028.4	1027.6
132.5°	1083.8	1084.1	1084.4	1084.5	1084.4	1084.1	1083.8	1083.6	1083.3	1082.3	1081.3
135°	1135.3	1134.8	1134.3	1134.0	1133.7	1133.2	1132.7	1132.2	1131.7	1130.7	1129.7
137.5°	1181.7	1181.9	1182.2	1182.3	1182.0	1181.5	1181.0	1180.5	1180.0	1178.7	1177.5
140°	1227.9	1227.6	1227.3	1227.2	1226.8	1226.1	1225.3	1224.6	1223.8	1223.3	1222.8
142.5°	1267.5	1267.5	1267.5	1267.5	1267.2	1266.7	1266.2	1265.7	1265.2	1265.0	1264.7
145°	1306.8	1306.3	1305.8	1305.5	1305.4	1305.1	1304.8	1304.6	1304.3	1304.3	1304.3
147.5°	1340.7	1340.4	1340.1	1340.0	1339.9	1339.6	1339.4	1339.1	1338.9	1339.1	1339.4
150°	1372.9	1372.7	1372.4	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.5	1372.8
152.5°	1401.6	1401.8	1402.1	1402.2	1401.9	1401.4	1400.9	1400.4	1399.9	1400.4	1400.9
155°	1426.8	1427.5	1428.3	1428.7	1428.2	1427.2	1426.1	1425.1	1424.1	1424.9	1425.6
157.5°	1448.5	1449.8	1451.1	1451.7	1451.1	1449.8	1448.5	1447.2	1445.9	1446.9	1448.0
160°	1469.8	1471.3	1472.8	1473.6	1472.8	1471.3	1469.8	1468.2	1466.7	1466.9	1467.2
162.5°	1486.4	1488.1	1489.9	1490.8	1490.0	1488.5	1487.0	1485.4	1483.9	1484.2	1484.4
165°	1502.4	1504.7	1507.0	1508.1	1507.1	1505.0	1503.0	1500.9	1498.9	1498.9	1498.9
167.5°	1514.4	1517.0	1519.5	1520.8	1519.6	1517.3	1515.0	1512.7	1510.4	1510.7	1510.9
170°	1524.7	1527.3	1529.8	1531.1	1530.1	1528.0	1526.0	1523.9	1521.9	1521.7	1521.4
172.5°	1531.0	1533.8	1536.6	1538.0	1537.0	1534.9	1532.9	1530.8	1528.8	1528.6	1528.3
175°	1536.1	1539.2	1542.3	1543.8	1542.6	1540.3	1538.0	1535.7	1533.4	1533.2	1532.9
177.5°	1538.4	1541.5	1544.6	1546.1	1545.1	1543.0	1541.0	1538.9	1536.9	1536.4	1535.9
180°	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9
2.5°	581.5	579.2	577.8	577.4	573.3	571.0	569.6	568.7	567.3	563.7	560.5
5°	603.4	597.0	593.8	590.2	583.8	576.5	570.5	566.9	562.3	555.0	548.1
7.5°	624.0	614.4	608.0	603.0	592.0	580.1	570.5	562.8	554.1	544.0	534.4
10°	645.4	629.9	621.7	613.9	597.9	582.4	568.7	557.3	545.0	531.7	521.2
12.5°	662.3	641.8	632.7	621.7	602.1	583.8	566.4	550.9	534.9	520.7	505.7
15°	682.0	656.4	645.9	631.7	604.8	581.0	558.7	541.8	525.3	504.3	488.3
17.5°	693.4	663.7	648.6	636.3	607.1	578.3	552.3	531.2	512.1	491.1	474.1
20°	704.8	671.0	654.1	636.8	602.1	571.4	544.0	518.9	498.8	476.0	458.6
22.5°	708.5	669.2	651.4	635.4	598.9	564.6	533.1	507.5	484.2	461.4	441.7
25°	708.5	668.7	647.7	627.2	588.8	553.6	522.1	494.2	468.2	445.4	425.7
27.5°	701.2	659.6	637.7	619.0	579.2	541.3	508.9	478.3	453.1	430.3	407.9
30°	692.0	646.4	624.4	602.1	563.7	527.6	492.4	464.1	437.6	411.6	391.5
32.5°	680.6	632.2	608.0	585.1	544.5	507.0	474.6	446.7	421.6	394.7	372.3
35°	664.2	611.2	584.2	564.1	524.9	486.0	455.0	427.6	403.3	375.5	351.3
37.5°	643.2	592.0	564.6	539.9	499.3	463.6	434.4	407.9	384.2	358.6	331.6
40°	618.5	565.1	541.3	515.3	472.3	438.5	411.1	387.4	363.6	339.4	313.4
42.5°	590.6	537.6	511.1	486.0	444.9	411.6	386.0	364.5	342.6	320.2	292.3
45°	557.3	507.5	481.9	458.2	418.4	384.2	360.9	340.3	321.6	298.7	274.1
47.5°	519.8	476.4	450.4	424.8	386.0	356.3	333.5	316.1	300.1	277.3	254.9
50°	483.3	440.3	419.3	393.3	357.7	329.8	306.5	291.9	279.6	257.2	237.1
52.5°	437.1	404.7	384.6	362.2	328.0	299.7	281.4	268.6	254.0	236.6	218.8
55°	396.5	366.3	350.4	329.3	295.5	270.4	254.9	243.0	231.6	216.1	201.9
57.5°	350.4	331.6	315.6	297.4	264.0	242.6	228.9	218.8	208.3	195.5	184.1
60°	301.9	293.3	277.7	263.1	234.8	216.1	204.6	195.5	185.5	175.0	165.4
62.5°	259.0	254.0	244.8	233.4	206.9	190.9	179.5	172.7	165.4	155.8	146.6
65°	218.3	216.1	207.4	199.2	180.9	166.7	156.7	152.6	144.3	137.0	128.8
67.5°	182.3	179.5	174.5	170.8	155.3	142.1	137.0	131.6	124.7	119.2	112.4
70°	145.7	145.3	142.1	137.5	129.3	119.7	114.7	111.0	104.1	100.0	95.0
72.5°	113.3	115.6	112.8	111.0	105.5	98.7	94.1	91.8	86.3	83.1	79.5
75°	84.5	86.3	87.7	84.5	83.1	79.9	75.8	73.5	70.8	66.2	64.9
77.5°	57.6	61.7	61.7	62.6	63.0	61.2	58.0	56.2	53.0	52.1	50.2
80°	37.9	41.6	42.0	42.9	44.3	44.3	42.0	41.6	38.4	37.9	36.5
82.5°	21.9	25.1	27.0	28.3	27.9	29.7	27.9	27.4	25.6	25.6	24.7
85°	11.9	12.3	13.2	14.2	15.1	16.0	16.0	15.5	15.1	14.6	13.7
87.5°	4.6	4.6	5.0	4.6	5.0	5.9	6.4	6.4	5.9	5.5	4.6
90°	19.2	17.1	16.1	14.7	11.9	9.1	6.3	3.5	6.3	9.1	11.9
92.5°	18.1	16.0	15.0	15.3	15.8	16.3	16.8	17.3	16.8	16.3	15.8
95°	24.6	24.3	24.2	28.5	37.2	45.9	54.6	63.3	54.6	45.9	37.2
97.5°	105.9	132.8	146.2	143.4	137.8	132.1	126.5	120.9	126.5	132.1	137.8
100°	156.6	191.9	209.5	207.2	202.6	198.0	193.4	188.8	193.4	198.0	202.6
102.5°	283.2	280.1	278.6	277.1	274.0	270.9	267.9	264.8	267.9	270.9	274.0
105°	355.3	354.0	353.4	352.6	351.1	349.6	348.0	346.5	348.0	349.6	351.1
107.5°	427.5	425.7	424.8	424.4	423.7	422.9	422.2	421.4	422.2	422.9	423.7
110°	503.1	501.6	500.8	500.4	499.6	498.9	498.1	497.3	498.1	498.9	499.6

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	578.7	578.2	577.9	577.1	575.6	574.1	572.5	571.0	572.5	574.1	575.6
115°	650.0	650.3	650.4	650.0	649.3	648.5	647.8	647.0	647.8	648.5	649.3
117.5°	720.7	719.9	719.5	719.0	718.0	716.9	715.9	714.9	715.9	716.9	718.0
120°	788.2	788.5	788.6	788.1	787.1	786.0	785.0	784.0	785.0	786.0	787.1
122.5°	851.6	851.1	850.8	850.5	850.0	849.5	849.0	848.5	849.0	849.5	850.0
125°	913.3	913.8	914.1	913.6	912.6	911.5	910.5	909.5	910.5	911.5	912.6
127.5°	971.2	969.9	969.3	969.2	968.9	968.7	968.4	968.2	968.4	968.7	968.9
130°	1026.9	1026.1	1025.7	1025.6	1025.3	1025.1	1024.8	1024.6	1024.8	1025.1	1025.3
132.5°	1080.2	1079.2	1078.7	1078.4	1077.9	1077.4	1076.9	1076.4	1076.9	1077.4	1077.9
135°	1128.6	1127.6	1127.1	1127.2	1127.5	1127.7	1128.0	1128.2	1128.0	1127.7	1127.5
137.5°	1176.2	1174.9	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3	1174.3
140°	1222.3	1221.8	1221.5	1221.2	1220.7	1220.2	1219.7	1219.2	1219.7	1220.2	1220.7
142.5°	1264.5	1264.2	1264.1	1263.6	1262.5	1261.5	1260.4	1259.4	1260.4	1261.5	1262.5
145°	1304.3	1304.3	1304.3	1303.9	1303.2	1302.4	1301.7	1300.9	1301.7	1302.4	1303.2
147.5°	1339.6	1339.9	1340.0	1339.2	1337.7	1336.2	1334.6	1333.1	1334.6	1336.2	1337.7
150°	1373.0	1373.3	1373.4	1372.9	1371.9	1370.8	1369.8	1368.8	1369.8	1370.8	1371.9
152.5°	1401.4	1401.9	1402.2	1401.8	1401.0	1400.3	1399.5	1398.7	1399.5	1400.3	1401.0
155°	1426.4	1427.1	1427.5	1427.4	1427.1	1426.9	1426.6	1426.4	1426.6	1426.9	1427.1
157.5°	1449.0	1450.1	1450.6	1450.6	1450.6	1450.6	1450.6	1450.6	1450.6	1450.6	1450.6
160°	1467.4	1467.7	1467.8	1468.2	1469.0	1469.7	1470.5	1471.3	1470.5	1469.7	1469.0
162.5°	1484.7	1485.0	1485.1	1485.6	1486.6	1487.7	1488.7	1489.7	1488.7	1487.7	1486.6
165°	1498.9	1498.9	1498.9	1499.5	1500.8	1502.1	1503.4	1504.7	1503.4	1502.1	1500.8
167.5°	1511.2	1511.5	1511.6	1512.2	1513.5	1514.8	1516.0	1517.3	1516.0	1514.8	1513.5
170°	1521.2	1520.9	1520.8	1521.6	1523.1	1524.6	1526.2	1527.7	1526.2	1524.6	1523.1
172.5°	1528.1	1527.8	1527.7	1528.5	1530.0	1531.5	1533.1	1534.6	1533.1	1531.5	1530.0
175°	1532.7	1532.4	1532.3	1533.1	1534.6	1536.1	1537.7	1539.2	1537.7	1536.1	1534.6
177.5°	1535.4	1534.9	1534.6	1535.5	1537.3	1539.1	1540.9	1542.7	1540.9	1539.1	1537.3
180°	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9
2.5°	557.7	556.8	555.9	552.3	549.1	543.6	539.0	537.2	536.7	537.2	535.8
5°	541.8	541.3	538.1	531.7	525.8	519.4	514.8	510.2	507.5	507.5	504.3
7.5°	526.7	523.5	520.7	512.5	505.7	497.0	490.1	486.0	483.7	478.7	478.7
10°	510.7	506.1	502.5	494.7	484.7	476.0	467.3	462.3	458.2	454.5	453.1
12.5°	494.7	491.1	484.2	476.0	465.9	455.0	445.8	442.2	432.6	424.8	425.3
15°	479.6	471.4	468.2	456.3	444.5	434.0	420.7	410.2	402.4	397.4	391.0
17.5°	462.7	454.5	448.6	438.5	423.0	406.5	393.8	379.6	371.8	363.1	359.0
20°	444.0	437.1	432.6	416.6	397.9	378.2	364.1	355.4	346.7	340.3	336.7
22.5°	428.0	419.3	413.9	392.4	371.8	352.2	341.2	333.9	326.6	321.1	319.3
25°	407.5	402.4	389.2	370.5	345.3	332.1	322.5	312.9	308.8	305.1	301.0
27.5°	390.6	378.2	369.1	344.4	328.9	313.8	304.2	296.9	291.9	288.2	285.0
30°	369.5	358.1	345.3	324.8	310.6	296.5	287.8	281.8	276.4	274.1	271.3
32.5°	347.6	337.1	324.8	308.3	291.0	280.0	273.2	266.8	263.1	260.8	257.6
35°	328.0	314.7	306.5	291.0	276.8	264.5	258.1	252.6	248.5	247.6	247.1
37.5°	307.0	296.9	289.1	273.2	261.3	250.8	244.8	238.9	236.6	236.2	234.3
40°	288.7	280.0	272.7	257.6	244.8	235.2	230.7	227.0	224.7	224.7	224.3
42.5°	272.7	263.6	256.3	242.6	231.1	222.5	217.4	213.8	212.9	213.3	212.9
45°	254.9	247.1	239.8	225.7	216.1	209.7	204.2	202.4	201.0	201.4	201.9
47.5°	238.0	231.6	224.3	212.9	201.9	195.0	191.9	190.0	190.0	190.0	190.9
50°	222.9	215.6	209.2	197.3	187.3	181.8	179.1	176.8	177.2	177.7	178.1
52.5°	205.1	198.7	194.1	182.3	175.0	168.1	164.9	165.4	164.9	164.9	165.8
55°	189.6	183.2	178.6	167.6	160.3	155.8	153.0	151.7	152.1	151.2	153.0
57.5°	172.2	166.7	163.5	153.0	146.6	142.5	140.2	138.0	138.9	138.4	138.0
60°	157.1	150.7	145.7	138.4	132.9	127.9	126.5	124.2	125.2	124.2	123.8
62.5°	139.8	134.8	131.1	123.8	119.2	115.1	111.9	110.5	110.1	108.7	107.3
65°	122.4	119.7	116.0	108.7	104.1	101.0	99.1	97.8	97.3	93.6	89.5
67.5°	106.4	104.6	101.0	95.5	91.4	88.2	85.4	83.1	80.4	77.7	75.4
70°	91.4	88.6	86.3	81.3	77.7	74.5	71.7	69.0	67.6	64.9	64.0
72.5°	76.7	74.0	71.7	67.1	64.0	60.8	59.8	56.6	55.3	54.8	54.8
75°	61.7	59.4	58.0	53.9	51.2	48.9	47.5	46.6	45.7	44.8	43.4
77.5°	47.0	45.7	44.8	42.0	39.7	38.4	37.9	34.7	33.8	32.9	32.0
80°	34.3	33.8	32.9	30.6	29.7	26.5	26.5	25.6	25.1	25.1	25.1
82.5°	23.3	22.4	21.9	19.6	19.2	18.7	18.3	17.8	18.3	17.8	18.3
85°	12.3	11.9	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.0	11.4
87.5°	4.6	4.6	4.6	4.6	4.1	4.6	4.6	4.1	4.6	4.6	4.6
90°	14.7	16.1	17.1	19.2	21.2	23.3	25.3	26.8	28.4	29.9	31.4
92.5°	15.3	15.0	16.0	18.1	20.1	22.2	24.2	25.7	27.3	28.8	30.3
95°	28.5	24.2	24.3	24.6	24.8	25.1	25.3	26.8	28.4	29.9	31.4
97.5°	143.4	146.2	132.8	105.9	79.0	52.2	25.3	26.6	27.9	29.2	30.5
100°	207.2	209.5	191.9	156.6	121.3	86.0	50.7	46.3	42.0	37.6	33.3
102.5°	277.1	278.6	280.1	283.2	286.3	289.3	292.4	234.8	177.3	119.7	62.2
105°	352.6	353.4	354.0	355.3	356.6	357.9	359.2	361.5	363.8	366.1	368.4
107.5°	424.4	424.8	425.7	427.5	429.3	431.1	432.9	434.2	435.4	436.7	438.0
110°	500.4	500.8	501.6	503.1	504.6	506.2	507.7	508.2	508.7	509.2	509.7

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	577.1	577.9	578.2	578.7	579.2	579.7	580.2	580.0	579.7	579.5	579.2
115°	650.0	650.4	650.3	650.0	649.8	649.5	649.3	649.8	650.3	650.8	651.3
117.5°	719.0	719.5	719.9	720.7	721.4	722.2	723.0	722.7	722.5	722.2	721.9
120°	788.1	788.6	788.5	788.2	787.9	787.7	787.4	787.9	788.4	788.9	789.4
122.5°	850.5	850.8	851.1	851.6	852.1	852.6	853.1	853.3	853.6	853.8	854.1
125°	913.6	914.1	913.8	913.3	912.8	912.3	911.8	912.6	913.3	914.1	914.8
127.5°	969.2	969.3	969.9	971.2	972.5	973.8	975.1	974.8	974.6	974.3	974.0
130°	1025.6	1025.7	1026.1	1026.9	1027.6	1028.4	1029.2	1029.5	1029.7	1030.0	1030.3
132.5°	1078.4	1078.7	1079.2	1080.2	1081.3	1082.3	1083.3	1083.6	1083.8	1084.1	1084.4
135°	1127.2	1127.1	1127.6	1128.6	1129.7	1130.7	1131.7	1132.2	1132.7	1133.2	1133.7
137.5°	1174.3	1174.3	1174.9	1176.2	1177.5	1178.7	1180.0	1180.5	1181.0	1181.5	1182.0
140°	1221.2	1221.5	1221.8	1222.3	1222.8	1223.3	1223.8	1224.6	1225.3	1226.1	1226.8
142.5°	1263.6	1264.1	1264.2	1264.5	1264.7	1265.0	1265.2	1265.7	1266.2	1266.7	1267.2
145°	1303.9	1304.3	1304.3	1304.3	1304.3	1304.3	1304.3	1304.6	1304.8	1305.1	1305.4
147.5°	1339.2	1340.0	1339.9	1339.6	1339.4	1339.1	1338.9	1339.1	1339.4	1339.6	1339.9
150°	1372.9	1373.4	1373.3	1373.0	1372.8	1372.5	1372.3	1372.3	1372.3	1372.3	1372.3
152.5°	1401.8	1402.2	1401.9	1401.4	1400.9	1400.4	1399.9	1400.4	1400.9	1401.4	1401.9
155°	1427.4	1427.5	1427.1	1426.4	1425.6	1424.9	1424.1	1425.1	1426.1	1427.2	1428.2
157.5°	1450.6	1450.6	1450.1	1449.0	1448.0	1446.9	1445.9	1447.2	1448.5	1449.8	1451.1
160°	1468.2	1467.8	1467.7	1467.4	1467.2	1466.9	1466.7	1468.2	1469.8	1471.3	1472.8
162.5°	1485.6	1485.1	1485.0	1484.7	1484.4	1484.2	1483.9	1485.4	1487.0	1488.5	1490.0
165°	1499.5	1498.9	1498.9	1498.9	1498.9	1498.9	1498.9	1500.9	1503.0	1505.0	1507.1
167.5°	1512.2	1511.6	1511.5	1511.2	1510.9	1510.7	1510.4	1512.7	1515.0	1517.3	1519.6
170°	1521.6	1520.8	1520.9	1521.2	1521.4	1521.7	1521.9	1523.9	1526.0	1528.0	1530.1
172.5°	1528.5	1527.7	1527.8	1528.1	1528.3	1528.6	1528.8	1530.8	1532.9	1534.9	1537.0
175°	1533.1	1532.3	1532.4	1532.7	1532.9	1533.2	1533.4	1535.7	1538.0	1540.3	1542.6
177.5°	1535.5	1534.6	1534.9	1535.4	1535.9	1536.4	1536.9	1538.9	1541.0	1543.0	1545.1
180°	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9
2.5°	535.8	537.6	535.4	536.7	533.5	533.1	533.5	533.5	534.0	534.4	534.9
5°	505.7	505.2	502.5	500.6	499.3	500.6	501.6	502.5	501.6	502.5	502.9
7.5°	477.3	476.0	474.6	471.4	472.3	471.4	474.1	472.8	472.8	475.1	476.9
10°	452.2	449.5	448.6	444.9	442.2	441.7	444.9	446.3	447.7	448.6	452.2
12.5°	419.8	415.7	412.5	413.9	406.1	409.3	410.2	408.4	413.9	420.2	416.6
15°	385.1	385.5	379.1	376.9	370.5	372.3	372.7	377.3	381.9	381.4	386.9
17.5°	359.5	356.8	351.3	350.8	348.1	349.4	349.0	352.6	351.3	353.6	358.1
20°	335.7	333.9	329.3	327.5	328.4	327.5	328.0	328.4	329.8	334.8	333.9
22.5°	317.0	314.7	314.7	312.4	309.7	308.8	311.1	312.4	314.3	315.2	317.5
25°	300.6	298.7	296.5	295.1	292.8	293.3	294.6	296.5	297.8	299.7	301.5
27.5°	283.7	283.7	281.4	280.9	280.0	279.6	281.4	282.3	282.3	283.7	285.5
30°	270.4	270.4	268.1	267.7	267.2	267.2	268.6	269.0	269.5	270.9	271.8
32.5°	257.6	257.2	256.3	256.7	256.3	256.7	256.7	257.2	258.1	258.5	260.4
35°	245.8	246.2	245.3	245.3	244.8	245.3	246.2	246.7	247.1	248.0	248.0
37.5°	234.3	235.2	234.8	236.2	236.2	236.2	236.2	237.1	237.1	237.1	236.6
40°	224.3	224.3	223.8	224.7	225.7	225.7	226.1	226.1	226.6	226.6	226.1
42.5°	212.9	213.8	215.1	215.6	216.5	216.1	217.4	217.0	217.4	216.5	215.6
45°	202.4	202.4	204.2	206.0	206.5	206.5	206.5	207.4	206.5	205.1	204.6
47.5°	190.9	191.9	192.8	195.0	195.5	195.5	195.5	195.5	194.6	194.6	194.6
50°	179.5	180.0	180.4	181.3	182.7	182.3	182.3	182.3	184.1	182.3	182.7
52.5°	165.8	166.3	166.7	168.6	168.1	168.1	168.6	168.6	169.9	169.5	168.6
55°	152.1	152.1	153.0	153.0	153.0	153.9	154.4	155.3	154.9	155.3	155.8
57.5°	138.4	137.5	137.0	137.0	138.4	138.0	138.4	138.4	140.2	141.1	141.6
60°	122.4	122.4	122.0	119.2	119.2	118.8	120.1	121.0	122.0	126.1	125.6
62.5°	106.0	104.1	102.3	102.8	100.0	101.4	100.5	101.4	104.1	107.3	107.8
65°	89.5	88.2	86.3	85.9	85.0	86.3	85.9	86.3	87.7	89.5	91.8
67.5°	74.9	74.5	73.5	73.1	73.1	73.1	74.0	74.0	74.5	75.8	77.2
70°	64.0	63.5	64.0	63.0	63.5	63.0	63.5	64.0	64.4	64.9	66.2
72.5°	53.9	53.9	53.9	53.0	53.9	53.4	53.4	53.9	54.4	54.8	55.7
75°	42.9	42.0	41.1	40.2	39.7	40.7	41.1	40.7	42.0	43.9	43.9
77.5°	32.4	32.0	32.0	32.0	32.4	32.0	32.9	32.4	32.9	32.9	33.8
80°	25.1	24.7	25.1	25.1	24.7	25.6	25.1	25.1	25.6	26.0	25.6
82.5°	18.3	18.7	18.3	18.3	18.3	19.2	18.3	18.3	18.3	18.7	18.7
85°	11.4	11.4	11.4	11.4	11.9	11.4	11.9	11.4	12.3	11.9	11.9
87.5°	4.1	4.6	5.0	5.0	5.0	5.0	4.6	5.0	5.5	5.0	5.5
90°	32.2	32.5	33.0	33.5	34.0	34.5	34.0	33.5	33.0	32.5	32.2
92.5°	31.1	31.1	31.1	31.1	31.1	31.1	31.1	31.1	31.1	31.1	31.1
95°	32.2	32.3	32.6	32.9	33.1	33.4	33.1	32.9	32.6	32.3	32.2
97.5°	31.1	31.2	31.5	31.7	32.0	32.2	32.0	31.7	31.5	31.2	31.1
100°	31.1	31.2	31.5	31.7	32.0	32.2	32.0	31.7	31.5	31.2	31.1
102.5°	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4
105°	369.5	364.9	355.7	346.5	337.3	328.1	337.3	346.5	355.7	364.9	369.5
107.5°	438.6	439.1	440.1	441.2	442.2	443.2	442.2	441.2	440.1	439.1	438.6
110°	510.0	510.4	511.1	511.9	512.6	513.4	512.6	511.9	511.1	510.4	510.0

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	579.1	579.6	580.6	581.7	582.7	583.7	582.7	581.7	580.6	579.6	579.1
115°	651.6	651.6	651.6	651.6	651.6	651.6	651.6	651.6	651.6	651.6	651.6
117.5°	721.8	721.8	721.8	721.8	721.8	721.8	721.8	721.8	721.8	721.8	721.8
120°	789.7	789.4	788.9	788.4	787.9	787.4	787.9	788.4	788.9	789.4	789.7
122.5°	854.2	853.9	853.4	852.9	852.4	851.9	852.4	852.9	853.4	853.9	854.2
125°	915.2	915.3	915.6	915.9	916.1	916.4	916.1	915.9	915.6	915.3	915.2
127.5°	973.9	973.8	973.5	973.3	973.0	972.8	973.0	973.3	973.5	973.8	973.9
130°	1030.4	1030.4	1030.4	1030.4	1030.4	1030.4	1030.4	1030.4	1030.4	1030.4	1030.4
132.5°	1084.5	1084.4	1084.1	1083.8	1083.6	1083.3	1083.6	1083.8	1084.1	1084.4	1084.5
135°	1134.0	1134.3	1134.8	1135.3	1135.8	1136.3	1135.8	1135.3	1134.8	1134.3	1134.0
137.5°	1182.3	1182.2	1181.9	1181.7	1181.4	1181.2	1181.4	1181.7	1181.9	1182.2	1182.3
140°	1227.2	1227.3	1227.6	1227.9	1228.1	1228.4	1228.1	1227.9	1227.6	1227.3	1227.2
142.5°	1267.5	1267.5	1267.5	1267.5	1267.5	1267.5	1267.5	1267.5	1267.5	1267.5	1267.5
145°	1305.5	1305.8	1306.3	1306.8	1307.3	1307.8	1307.3	1306.8	1306.3	1305.8	1305.5
147.5°	1340.0	1340.1	1340.4	1340.7	1340.9	1341.2	1340.9	1340.7	1340.4	1340.1	1340.0
150°	1372.3	1372.4	1372.7	1372.9	1373.2	1373.4	1373.2	1372.9	1372.7	1372.4	1372.3
152.5°	1402.2	1402.1	1401.8	1401.6	1401.3	1401.1	1401.3	1401.6	1401.8	1402.1	1402.2
155°	1428.7	1428.3	1427.5	1426.8	1426.0	1425.2	1426.0	1426.8	1427.5	1428.3	1428.7
157.5°	1451.7	1451.1	1449.8	1448.5	1447.2	1445.9	1447.2	1448.5	1449.8	1451.1	1451.7
160°	1473.6	1472.8	1471.3	1469.8	1468.2	1466.7	1468.2	1469.8	1471.3	1472.8	1473.6
162.5°	1490.8	1489.9	1488.1	1486.4	1484.6	1482.8	1484.6	1486.4	1488.1	1489.9	1490.8
165°	1508.1	1507.0	1504.7	1502.4	1500.1	1497.8	1500.1	1502.4	1504.7	1507.0	1508.1
167.5°	1520.8	1519.5	1517.0	1514.4	1511.9	1509.3	1511.9	1514.4	1517.0	1519.5	1520.8
170°	1531.1	1529.8	1527.3	1524.7	1522.2	1519.6	1522.2	1524.7	1527.3	1529.8	1531.1
172.5°	1538.0	1536.6	1533.8	1531.0	1528.2	1525.4	1528.2	1531.0	1533.8	1536.6	1538.0
175°	1543.8	1542.3	1539.2	1536.1	1533.1	1530.0	1533.1	1536.1	1539.2	1542.3	1543.8
177.5°	1546.1	1544.6	1541.5	1538.4	1535.4	1532.3	1535.4	1538.4	1541.5	1544.6	1546.1
180°	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9	566.9
2.5°	536.7	539.0	538.1	534.9	536.3	539.0	541.8	545.4	547.7	549.5	550.4
5°	505.2	509.3	508.4	508.4	510.2	514.8	519.4	527.1	529.9	533.1	537.6
7.5°	477.3	480.5	483.3	484.2	486.9	492.9	498.8	507.5	514.3	518.0	520.7
10°	452.7	455.0	459.1	461.4	464.1	471.4	480.1	489.2	496.1	502.5	506.1
12.5°	421.2	430.3	435.8	439.4	443.1	454.1	460.9	471.0	479.2	485.1	490.6
15°	386.0	397.0	400.1	414.3	423.4	432.1	442.6	454.5	462.3	469.1	476.4
17.5°	356.3	364.1	367.7	382.8	390.6	404.3	419.3	434.4	446.3	451.3	458.6
20°	337.6	341.7	349.0	354.0	362.2	378.2	394.7	412.9	430.8	435.8	443.1
22.5°	318.4	323.9	328.9	335.7	342.1	353.1	369.5	389.6	408.8	418.0	426.6
25°	301.0	306.5	309.7	317.0	323.0	333.9	345.3	365.9	388.7	396.5	410.2
27.5°	287.3	290.5	296.0	299.2	306.0	316.1	326.6	342.1	364.5	377.8	391.0
30°	273.6	275.9	280.5	285.0	290.1	296.9	308.8	323.9	344.4	355.8	369.1
32.5°	259.9	263.6	266.3	269.5	275.0	283.2	291.4	306.0	322.5	335.3	348.5
35°	248.5	249.9	253.5	257.2	260.8	268.1	276.8	291.0	305.6	315.6	327.5
37.5°	236.2	238.4	241.2	242.6	248.5	253.1	262.2	273.2	290.5	296.9	308.8
40°	226.6	226.1	228.9	231.1	233.9	241.2	246.7	258.5	272.2	282.3	289.6
42.5°	214.7	214.7	215.6	218.3	222.0	226.6	233.0	243.0	257.2	264.5	273.2
45°	205.1	203.7	204.2	206.0	208.3	212.9	219.3	227.9	242.1	248.0	257.2
47.5°	193.7	192.3	192.3	194.1	196.0	199.2	204.2	214.2	225.7	233.4	240.3
50°	180.9	181.3	180.9	182.3	183.2	186.4	191.9	200.1	210.6	217.0	224.7
52.5°	169.0	168.1	167.6	168.6	170.4	172.7	178.6	185.9	196.0	202.4	209.2
55°	154.4	155.3	155.3	155.3	158.0	159.0	163.5	170.8	180.9	185.9	192.3
57.5°	141.1	140.7	141.6	141.1	143.4	146.6	150.3	155.8	165.8	170.8	176.8
60°	126.5	127.0	127.4	127.4	129.3	132.5	136.6	141.6	149.8	154.9	160.3
62.5°	108.7	111.0	113.3	114.2	116.9	119.2	122.0	127.4	134.8	138.4	143.4
65°	91.8	95.0	98.2	100.5	102.3	104.6	108.3	113.3	119.2	122.9	127.9
67.5°	77.2	79.5	83.6	85.9	89.5	92.3	94.6	98.7	106.0	107.3	111.5
70°	66.7	67.6	69.4	71.3	75.4	77.7	80.4	84.5	90.0	93.2	95.5
72.5°	56.2	56.6	57.6	59.4	61.2	64.0	67.1	70.8	75.8	77.2	80.4
75°	44.8	47.5	47.5	48.9	50.2	51.6	54.4	58.0	61.2	63.5	65.3
77.5°	33.3	34.7	35.6	37.9	39.7	41.1	42.9	45.7	47.5	49.3	50.7
80°	26.0	26.5	27.0	27.0	27.9	29.7	31.5	33.3	35.6	36.5	37.9
82.5°	19.2	19.2	19.2	20.1	20.6	21.0	21.0	21.9	24.2	25.1	26.5
85°	12.3	12.3	12.3	12.3	12.8	13.2	13.7	14.2	14.2	14.2	15.1
87.5°	5.0	5.9	5.5	5.9	5.9	5.9	5.9	6.4	6.4	6.9	6.9
90°	31.4	29.9	28.4	26.8	25.3	23.3	21.2	19.2	17.1	16.1	14.7
92.5°	30.3	28.8	27.3	25.7	24.2	22.2	20.1	18.1	16.0	15.0	15.3
95°	31.4	29.9	28.4	26.8	25.3	25.1	24.8	24.6	24.3	24.2	28.5
97.5°	30.5	29.2	27.9	26.6	25.3	52.2	79.0	105.9	132.8	146.2	143.4
100°	33.3	37.6	42.0	46.3	50.7	86.0	121.3	156.6	191.9	209.5	207.2
102.5°	62.2	119.7	177.3	234.8	292.4	289.3	286.3	283.2	280.1	278.6	277.1
105°	368.4	366.1	363.8	361.5	359.2	357.9	356.6	355.3	354.0	353.4	352.6
107.5°	438.0	436.7	435.4	434.2	432.9	431.1	429.3	427.5	425.7	424.8	424.4
110°	509.7	509.2	508.7	508.2	507.7	506.2	504.6	503.1	501.6	500.8	500.4

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	579.2	579.5	579.7	580.0	580.2	579.7	579.2	578.7	578.2	577.9	577.1
115°	651.3	650.8	650.3	649.8	649.3	649.5	649.8	650.0	650.3	650.4	650.0
117.5°	721.9	722.2	722.5	722.7	723.0	722.2	721.4	720.7	719.9	719.5	719.0
120°	789.4	788.9	788.4	787.9	787.4	787.7	787.9	788.2	788.5	788.6	788.1
122.5°	854.1	853.8	853.6	853.3	853.1	852.6	852.1	851.6	851.1	850.8	850.5
125°	914.8	914.1	913.3	912.6	911.8	912.3	912.8	913.3	913.8	914.1	913.6
127.5°	974.0	974.3	974.6	974.8	975.1	973.8	972.5	971.2	969.9	969.3	969.2
130°	1030.3	1030.0	1029.7	1029.5	1029.2	1028.4	1027.6	1026.9	1026.1	1025.7	1025.6
132.5°	1084.4	1084.1	1083.8	1083.6	1083.3	1082.3	1081.3	1080.2	1079.2	1078.7	1078.4
135°	1133.7	1133.2	1132.7	1132.2	1131.7	1130.7	1129.7	1128.6	1127.6	1127.1	1127.2
137.5°	1182.0	1181.5	1181.0	1180.5	1180.0	1178.7	1177.5	1176.2	1174.9	1174.3	1174.3
140°	1226.8	1226.1	1225.3	1224.6	1223.8	1223.3	1222.8	1222.3	1221.8	1221.5	1221.2
142.5°	1267.2	1266.7	1266.2	1265.7	1265.2	1265.0	1264.7	1264.5	1264.2	1264.1	1263.6
145°	1305.4	1305.1	1304.8	1304.6	1304.3	1304.3	1304.3	1304.3	1304.3	1304.3	1303.9
147.5°	1339.9	1339.6	1339.4	1339.1	1338.9	1339.1	1339.4	1339.6	1339.9	1340.0	1339.2
150°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.5	1372.8	1373.0	1373.3	1373.4	1372.9
152.5°	1401.9	1401.4	1400.9	1400.4	1399.9	1400.4	1400.9	1401.4	1401.9	1402.2	1401.8
155°	1428.2	1427.2	1426.1	1425.1	1424.1	1424.9	1425.6	1426.4	1427.1	1427.5	1427.4
157.5°	1451.1	1449.8	1448.5	1447.2	1445.9	1446.9	1448.0	1449.0	1450.1	1450.6	1450.6
160°	1472.8	1471.3	1469.8	1468.2	1466.7	1466.9	1467.2	1467.4	1467.7	1467.8	1468.2
162.5°	1490.0	1488.5	1487.0	1485.4	1483.9	1484.2	1484.4	1484.7	1485.0	1485.1	1485.6
165°	1507.1	1505.0	1503.0	1500.9	1498.9	1498.9	1498.9	1498.9	1498.9	1498.9	1499.5
167.5°	1519.6	1517.3	1515.0	1512.7	1510.4	1510.7	1510.9	1511.2	1511.5	1511.6	1512.2
170°	1530.1	1528.0	1526.0	1523.9	1521.9	1521.7	1521.4	1521.2	1520.9	1520.8	1521.6
172.5°	1537.0	1534.9	1532.9	1530.8	1528.8	1528.6	1528.3	1528.1	1527.8	1527.7	1528.5
175°	1542.6	1540.3	1538.0	1535.7	1533.4	1533.2	1532.9	1532.7	1532.4	1532.3	1533.1
177.5°	1545.1	1543.0	1541.0	1538.9	1536.9	1536.4	1535.9	1535.4	1534.9	1534.6	1535.5
180°	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2	1539.2

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	566.9	566.9	566.9	566.9
2.5°	554.1	556.8	561.4	567.8
5°	541.3	549.1	556.4	566.0
7.5°	529.9	539.0	549.1	562.8
10°	516.6	528.1	540.8	557.7
12.5°	501.1	517.1	531.7	550.0
15°	489.7	501.6	520.3	541.8
17.5°	473.7	489.7	508.4	532.6
20°	458.6	475.5	496.5	521.7
22.5°	442.6	461.8	482.8	509.8
25°	426.2	446.7	467.8	496.5
27.5°	411.1	429.8	453.6	482.8
30°	392.8	414.3	437.1	467.8
32.5°	375.0	397.4	420.7	451.3
35°	355.8	378.2	403.8	433.0
37.5°	337.1	361.8	385.1	413.4
40°	316.6	342.1	366.3	395.1
42.5°	296.5	323.0	347.2	371.8
45°	277.7	303.8	325.7	349.0
47.5°	259.9	283.2	305.6	326.6
50°	242.6	262.2	282.8	300.1
52.5°	224.3	243.0	259.5	275.0
55°	207.8	222.5	237.1	251.2
57.5°	188.2	202.8	215.6	226.6
60°	171.8	180.9	193.2	204.6
62.5°	153.0	163.5	173.1	180.4
65°	134.8	143.9	151.2	157.6
67.5°	119.2	124.7	130.2	137.0
70°	100.5	105.1	111.5	116.5
72.5°	84.5	88.2	91.4	97.3
75°	68.5	71.7	73.5	79.0
77.5°	53.0	56.2	57.6	60.8
80°	40.7	41.1	42.9	45.7
82.5°	27.9	28.8	29.2	31.5
85°	16.0	18.3	17.8	18.7
87.5°	6.9	7.3	8.2	9.1
90°	11.9	9.1	6.3	3.5
92.5°	15.8	16.3	16.8	17.3
95°	37.2	45.9	54.6	63.3
97.5°	137.8	132.1	126.5	120.9
100°	202.6	198.0	193.4	188.8
102.5°	274.0	270.9	267.9	264.8
105°	351.1	349.6	348.0	346.5
107.5°	423.7	422.9	422.2	421.4
110°	499.6	498.9	498.1	497.3

TEST NUMBER: P1013310

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	575.6	574.1	572.5	571.0
115°	649.3	648.5	647.8	647.0
117.5°	718.0	716.9	715.9	714.9
120°	787.1	786.0	785.0	784.0
122.5°	850.0	849.5	849.0	848.5
125°	912.6	911.5	910.5	909.5
127.5°	968.9	968.7	968.4	968.2
130°	1025.3	1025.1	1024.8	1024.6
132.5°	1077.9	1077.4	1076.9	1076.4
135°	1127.5	1127.7	1128.0	1128.2
137.5°	1174.3	1174.3	1174.3	1174.3
140°	1220.7	1220.2	1219.7	1219.2
142.5°	1262.5	1261.5	1260.4	1259.4
145°	1303.2	1302.4	1301.7	1300.9
147.5°	1337.7	1336.2	1334.6	1333.1
150°	1371.9	1370.8	1369.8	1368.8
152.5°	1401.0	1400.3	1399.5	1398.7
155°	1427.1	1426.9	1426.6	1426.4
157.5°	1450.6	1450.6	1450.6	1450.6
160°	1469.0	1469.7	1470.5	1471.3
162.5°	1486.6	1487.7	1488.7	1489.7
165°	1500.8	1502.1	1503.4	1504.7
167.5°	1513.5	1514.8	1516.0	1517.3
170°	1523.1	1524.6	1526.2	1527.7
172.5°	1530.0	1531.5	1533.1	1534.6
175°	1534.6	1536.1	1537.7	1539.2
177.5°	1537.3	1539.1	1540.9	1542.7
180°	1539.2	1539.2	1539.2	1539.2

(END OF REPORT)