

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013332

Luminaire Tested: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013332
REPORT IS A COMBINATION OF REPORTS P999349 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3665.0 lumens
Efficiency: N/A
Efficacy: 129.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	39	39	39
1	95	91	88	84	87	83	80	77	68	66	64	53	52	51	40	40	39	33	33	33
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28	28	28
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24	24	24
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21	21	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18	18	18
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16	16	16
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17	14	14	14
8	53	41	34	28	48	38	31	27	31	26	23	26	22	19	20	17	15	13	13	13
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	18	16	14	12	12	12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11	11	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4484	4484	4484	4484
5°	4484	5067	4491	3872
10°	4460	5841	4457	3368
15°	4407	6574	4407	2820
20°	4351	7127	4328	2483
25°	4283	7157	4264	2243
30°	4211	6086	4179	2077
35°	4109	4592	4057	1954
40°	3996	3328	3917	1858
45°	3808	2529	3714	1773
50°	3586	2044	3488	1648
55°	3345	1693	3235	1481
60°	3103	1431	2964	1232
65°	2800	1166	2710	979
70°	2521	946	2403	795
75°	2210	682	2055	583
80°	1822	451	1657	428
85°	1324	233	1099	233

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 5613 cd/sqm

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	1.5
10°-20°	160.8	4.4
20°-30°	251.9	6.9
30°-40°	279.7	7.6
40°-50°	247.8	6.8
50°-60°	193.1	5.3
60°-70°	126.3	3.4
70°-80°	62.0	1.7
80°-90°	16.6	0.5
90°-100°	24.4	0.7
100°-110°	160.6	4.4
110°-120°	306.7	8.4
120°-130°	389.4	10.6
130°-140°	416.5	11.4
140°-150°	389.5	10.6
150°-160°	314.1	8.6
160°-170°	202.6	5.5
170°-180°	69.8	1.9
0°-30°	465.9	12.7
0°-40°	745.6	20.3
0°-60°	1186.6	32.4
0°-90°	1391.5	38.0
90°-120°	491.7	13.4
90°-150°	1687.0	46.0
90°-180°	2273.0	62.0
0°-180°	3665.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	550	550	550	550	550	
5°	549	635	550	486	549	52
15°	526	842	526	361	526	148
25°	482	908	479	284	482	222
35°	420	559	415	238	420	263
45°	338	286	330	200	338	261
55°	244	171	236	149	244	218
65°	153	100	148	84	153	152
75°	77	46	71	39	77	81
85°	18	11	15	11	18	21
90°	2	16	2	16	2	3
95°	30	16	30	16	30	37
105°	165	157	165	157	165	173
115°	309	311	309	311	309	304
125°	434	437	434	437	434	388
135°	538	542	538	542	538	415
145°	621	624	621	624	621	388
155°	681	680	681	680	681	314
165°	718	715	718	715	718	203
175°	735	730	735	730	735	70
180°	735	735	735	735	735	

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9
2.5°	550.8	555.6	558.3	560.5	564.9	566.7	570.2	571.1	574.7	574.2	572.9
5°	549.0	557.4	563.6	570.2	578.2	582.7	587.5	594.6	598.2	603.0	606.1
7.5°	545.9	557.4	567.6	577.8	590.6	597.7	603.9	615.0	624.3	632.3	641.1
10°	541.0	555.6	570.7	584.4	602.2	610.6	619.9	636.3	649.1	660.2	674.4
12.5°	533.5	553.9	570.7	589.3	611.9	623.4	635.8	655.3	670.4	688.6	706.3
15°	525.5	548.1	570.2	594.6	620.3	633.6	646.0	672.2	695.2	716.0	735.5
17.5°	516.6	541.4	565.8	592.8	623.9	640.3	654.9	686.3	711.6	738.6	758.1
20°	506.0	533.0	560.9	591.1	626.1	644.2	660.6	696.5	724.4	753.7	778.1
22.5°	494.5	523.7	554.3	587.1	623.4	643.4	662.4	701.0	733.3	760.3	793.1
25°	481.6	512.6	544.1	578.7	619.4	641.1	660.6	698.7	733.3	768.8	800.7
27.5°	468.3	500.2	533.0	569.4	611.0	632.3	654.4	691.2	731.5	770.1	802.4
30°	453.7	484.7	519.3	553.9	598.2	619.4	642.0	681.9	725.8	764.3	799.3
32.5°	437.8	469.7	502.5	538.3	581.8	604.8	625.6	670.8	715.6	753.7	786.5
35°	420.0	450.2	481.2	518.0	560.9	581.8	606.6	653.5	698.7	739.1	760.3
37.5°	401.0	429.8	458.6	494.9	536.1	561.4	585.8	633.2	681.0	708.0	719.1
40°	383.3	408.5	433.8	468.8	510.4	536.6	561.4	610.6	652.7	673.5	665.1
42.5°	360.7	386.8	409.4	441.8	483.8	508.2	533.5	584.4	618.5	627.0	606.1
45°	338.5	360.2	381.9	413.4	457.7	478.5	505.6	553.0	581.3	573.8	543.2
47.5°	316.8	334.5	354.9	385.5	425.4	450.2	475.4	516.6	536.6	525.9	483.4
50°	291.1	308.8	330.1	356.7	395.2	419.2	439.1	477.2	492.3	466.1	414.7
52.5°	266.7	282.2	300.4	325.2	362.0	383.7	405.4	438.2	443.1	413.0	358.9
55°	243.7	256.1	275.2	295.1	328.8	351.8	366.9	394.8	393.5	355.8	309.3
57.5°	219.8	231.3	244.1	265.0	296.9	314.1	330.5	354.9	342.1	310.2	264.1
60°	198.5	205.1	218.0	237.9	265.0	280.0	292.9	306.2	295.1	260.5	225.1
62.5°	175.0	182.6	191.9	207.8	231.7	245.9	255.2	261.0	249.5	222.9	190.5
65°	152.9	159.5	169.3	183.4	201.6	212.2	217.1	221.1	214.9	184.8	159.1
67.5°	132.9	137.4	146.2	155.5	175.0	177.7	184.3	186.1	173.7	150.6	130.3
70°	113.0	117.4	121.4	132.5	141.3	146.2	147.5	147.5	135.1	120.1	103.2
72.5°	94.4	97.0	101.0	108.6	113.4	117.0	118.7	116.5	105.0	92.6	80.2
75°	76.7	78.0	81.5	86.4	90.4	89.1	88.6	86.0	77.5	68.7	61.6
77.5°	58.9	59.8	63.8	65.1	65.1	66.5	64.7	62.0	54.9	48.3	45.2
80°	44.3	45.6	46.1	47.0	46.1	46.1	44.8	40.3	36.8	33.7	31.5
82.5°	30.6	31.5	31.9	30.6	31.5	30.1	27.9	24.8	22.6	22.2	21.3
85°	18.2	18.6	18.2	18.2	16.8	16.4	14.6	14.2	13.3	13.3	12.8
87.5°	8.9	8.4	7.5	6.6	6.6	6.2	6.6	5.8	6.6	6.2	5.8
90°	1.6	3.0	4.3	5.7	7.0	7.7	8.2	9.2	10.1	11.1	12.1
92.5°	8.2	8.0	7.7	7.5	7.2	7.1	7.6	8.6	9.5	10.5	11.5
95°	30.2	26.0	21.9	17.7	13.6	11.5	11.6	11.7	11.8	12.0	12.1
97.5°	57.7	60.4	63.1	65.8	68.5	69.8	63.4	50.6	37.7	24.9	12.1
100°	90.1	92.3	94.5	96.7	98.9	100.0	91.6	74.7	57.9	41.0	24.2
102.5°	126.4	127.9	129.3	130.8	132.3	133.0	133.7	135.2	136.7	138.1	139.6
105°	165.4	166.1	166.9	167.6	168.3	168.7	169.0	169.6	170.3	170.9	171.5
107.5°	201.1	201.5	201.9	202.2	202.6	202.8	203.2	204.1	204.9	205.8	206.6
110°	237.4	237.8	238.1	238.5	238.8	239.0	239.4	240.1	240.8	241.6	242.3

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	272.6	273.3	274.1	274.8	275.5	275.9	276.0	276.3	276.5	276.8	277.0
115°	308.8	309.2	309.6	309.9	310.3	310.5	310.4	310.3	310.2	310.0	309.9
117.5°	341.3	341.8	342.3	342.8	343.3	343.5	343.7	344.0	344.4	344.7	345.1
120°	374.2	374.7	375.2	375.7	376.2	376.4	376.3	376.2	376.1	376.0	375.9
122.5°	405.0	405.2	405.5	405.7	406.0	406.1	406.2	406.5	406.7	407.0	407.2
125°	434.1	434.6	435.1	435.6	436.1	436.3	436.2	435.9	435.7	435.4	435.2
127.5°	462.2	462.3	462.4	462.5	462.6	462.7	463.0	463.6	464.3	464.9	465.5
130°	489.1	489.2	489.3	489.4	489.5	489.6	489.8	490.2	490.5	490.9	491.3
132.5°	513.8	514.0	514.3	514.5	514.8	514.9	515.1	515.6	516.1	516.6	517.1
135°	538.5	538.4	538.3	538.2	538.1	538.0	538.2	538.7	539.2	539.7	540.2
137.5°	560.5	560.5	560.5	560.5	560.5	560.5	560.8	561.4	562.1	562.7	563.3
140°	582.0	582.2	582.5	582.7	583.0	583.1	583.2	583.4	583.7	583.9	584.1
142.5°	601.2	601.7	602.2	602.7	603.2	603.4	603.5	603.6	603.7	603.8	603.9
145°	621.0	621.4	621.7	622.1	622.4	622.6	622.6	622.6	622.6	622.6	622.6
147.5°	636.4	637.1	637.9	638.6	639.3	639.7	639.6	639.5	639.4	639.2	639.1
150°	653.4	653.9	654.4	654.9	655.4	655.6	655.5	655.4	655.3	655.1	655.0
152.5°	667.7	668.1	668.4	668.8	669.1	669.3	669.2	668.9	668.7	668.4	668.2
155°	680.9	681.0	681.1	681.2	681.3	681.4	681.2	680.9	680.5	680.2	679.8
157.5°	692.4	692.4	692.4	692.4	692.4	692.4	692.2	691.7	691.2	690.7	690.2
160°	702.3	701.9	701.5	701.2	700.8	700.6	700.5	700.4	700.3	700.2	700.1
162.5°	711.1	710.6	710.1	709.6	709.1	708.9	708.8	708.7	708.6	708.4	708.3
165°	718.2	717.6	717.0	716.4	715.8	715.5	715.5	715.5	715.5	715.5	715.5
167.5°	724.3	723.7	723.1	722.4	721.8	721.5	721.4	721.3	721.2	721.1	721.0
170°	729.2	728.5	727.7	727.0	726.3	725.9	726.0	726.1	726.2	726.4	726.5
172.5°	732.5	731.8	731.0	730.3	729.6	729.2	729.3	729.4	729.5	729.7	729.8
175°	734.7	734.0	733.2	732.5	731.8	731.4	731.5	731.6	731.7	731.9	732.0
177.5°	736.4	735.5	734.7	733.8	732.9	732.5	732.6	732.9	733.1	733.4	733.6
180°	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9
2.5°	576.5	581.3	581.8	586.2	584.9	582.7	586.6	584.0	589.3	587.5	589.7
5°	610.1	616.8	622.5	626.1	632.3	631.0	637.6	635.4	640.3	635.4	641.6
7.5°	649.6	660.6	666.4	675.7	678.4	678.8	686.8	688.6	691.7	688.6	692.1
10°	688.1	701.4	714.7	722.2	727.1	733.7	740.8	743.9	746.2	743.1	745.3
12.5°	723.1	743.9	758.6	773.6	777.2	782.9	790.5	789.6	798.4	796.7	800.7
15°	755.5	778.5	796.2	808.2	817.9	822.8	837.0	837.9	837.4	841.9	839.2
17.5°	784.3	803.8	829.0	844.5	856.5	856.5	864.5	880.9	879.5	879.1	881.7
20°	807.7	829.9	853.4	879.5	889.3	891.0	902.1	910.5	911.9	911.9	911.9
22.5°	825.5	851.6	876.9	895.5	903.0	909.2	919.0	924.3	926.0	925.2	926.0
25°	834.3	859.1	884.8	901.7	906.1	909.7	910.5	913.6	913.2	907.9	911.0
27.5°	836.1	860.0	876.9	881.3	879.1	876.9	862.7	864.0	860.0	852.1	855.2
30°	828.1	841.0	840.5	826.8	822.8	813.5	800.7	781.6	766.1	759.4	761.7
32.5°	799.3	799.3	783.4	752.4	738.6	721.8	698.7	681.5	661.1	656.7	665.1
35°	759.4	736.8	707.6	666.8	646.0	633.6	593.7	581.3	564.0	559.2	563.2
37.5°	697.4	659.8	617.2	579.1	561.4	539.2	504.2	486.5	474.1	465.7	469.7
40°	627.9	582.2	537.9	490.9	471.4	453.3	427.1	411.2	391.2	392.1	393.5
42.5°	561.4	507.8	458.1	414.7	396.1	381.1	362.9	343.4	336.3	334.1	331.9
45°	490.9	433.8	387.3	354.9	338.1	323.9	307.1	296.0	287.6	285.8	288.0
47.5°	424.5	376.2	331.9	301.7	288.0	280.9	267.6	257.4	252.1	247.7	250.3
50°	364.2	319.0	283.6	258.3	248.6	243.7	231.3	226.0	220.7	219.3	218.9
52.5°	314.6	276.0	245.5	225.1	217.6	214.9	205.6	198.1	193.6	195.0	195.8
55°	269.4	236.6	212.7	196.3	190.1	187.0	180.3	175.0	171.9	170.6	171.5
57.5°	229.5	201.2	183.9	170.6	165.7	164.4	157.3	155.5	153.3	152.0	152.0
60°	193.2	173.2	157.3	149.8	144.4	143.1	137.8	135.6	135.1	133.8	132.9
62.5°	162.6	146.2	135.1	127.2	124.9	124.5	121.0	118.3	117.0	116.1	116.1
65°	136.0	124.1	114.8	109.0	107.2	106.3	102.4	101.5	100.6	99.7	99.3
67.5°	113.4	102.8	96.1	92.2	89.9	90.4	88.2	86.4	86.4	86.0	85.5
70°	91.7	85.1	79.3	77.1	76.2	75.3	74.4	73.1	72.7	72.7	72.7
72.5°	72.2	67.8	64.7	63.4	62.5	61.6	60.7	60.7	60.7	60.3	60.3
75°	55.4	53.6	51.4	50.1	50.1	51.0	49.6	48.3	47.0	46.1	46.5
77.5°	41.6	40.8	39.4	37.2	37.7	36.8	36.8	35.9	36.3	36.3	35.4
80°	30.6	29.2	28.8	27.5	27.9	27.5	27.0	27.0	26.1	26.1	26.1
82.5°	21.3	19.9	19.9	19.5	19.1	19.1	18.6	18.6	19.1	18.2	18.2
85°	12.8	12.4	12.4	11.5	11.5	11.5	11.5	12.0	11.5	11.1	11.1
87.5°	5.8	6.2	5.8	5.3	5.3	5.3	4.9	4.9	4.4	4.9	4.9
90°	12.8	13.6	14.3	15.0	15.4	15.5	15.8	16.0	16.3	16.5	16.3
92.5°	12.2	13.0	13.7	14.4	14.8	14.8	14.8	14.8	14.8	14.8	14.8
95°	12.8	13.6	14.3	15.0	15.4	15.5	15.6	15.7	15.8	15.9	15.8
97.5°	12.7	13.3	13.9	14.5	14.8	14.9	15.0	15.1	15.3	15.4	15.3
100°	22.1	20.0	17.9	15.8	14.8	14.9	15.0	15.1	15.3	15.4	15.3
102.5°	112.1	84.6	57.1	29.6	15.9	15.9	15.9	15.9	15.9	15.9	15.9
105°	172.6	173.7	174.8	175.9	176.4	174.2	169.8	165.4	161.0	156.6	161.0
107.5°	207.2	207.8	208.5	209.1	209.4	209.6	210.1	210.6	211.1	211.6	211.1
110°	242.5	242.8	243.0	243.3	243.4	243.6	244.0	244.3	244.7	245.1	244.7

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	276.9	276.7	276.6	276.5	276.4	276.6	277.1	277.6	278.1	278.6	278.1
115°	310.1	310.4	310.6	310.9	311.0	311.0	311.0	311.0	311.0	311.0	311.0
117.5°	345.0	344.9	344.8	344.7	344.6	344.6	344.6	344.6	344.6	344.6	344.6
120°	376.1	376.4	376.6	376.9	377.0	376.9	376.6	376.4	376.1	375.9	376.1
122.5°	407.3	407.5	407.6	407.7	407.8	407.7	407.4	407.2	406.9	406.7	406.9
125°	435.6	436.0	436.3	436.7	436.9	437.0	437.1	437.2	437.3	437.4	437.3
127.5°	465.4	465.2	465.1	465.0	464.9	464.8	464.7	464.6	464.5	464.4	464.5
130°	491.4	491.5	491.6	491.7	491.8	491.8	491.8	491.8	491.8	491.8	491.8
132.5°	517.2	517.4	517.5	517.6	517.7	517.6	517.5	517.4	517.2	517.1	517.2
135°	540.4	540.7	540.9	541.2	541.3	541.4	541.7	541.9	542.2	542.4	542.2
137.5°	563.5	563.8	564.0	564.3	564.4	564.3	564.2	564.1	563.9	563.8	563.9
140°	584.5	584.9	585.2	585.6	585.8	585.9	586.0	586.1	586.2	586.3	586.2
142.5°	604.1	604.4	604.6	604.9	605.0	605.0	605.0	605.0	605.0	605.0	605.0
145°	622.7	622.9	623.0	623.1	623.2	623.3	623.6	623.8	624.1	624.3	624.1
147.5°	639.2	639.4	639.5	639.6	639.7	639.8	639.9	640.0	640.1	640.2	640.1
150°	655.0	655.0	655.0	655.0	655.0	655.1	655.2	655.3	655.5	655.6	655.5
152.5°	668.4	668.7	668.9	669.2	669.3	669.2	669.1	669.0	668.9	668.8	668.9
155°	680.3	680.8	681.3	681.8	682.0	681.8	681.4	681.1	680.7	680.3	680.7
157.5°	690.8	691.4	692.1	692.7	693.0	692.7	692.1	691.4	690.8	690.2	690.8
160°	700.8	701.6	702.3	703.0	703.4	703.0	702.3	701.6	700.8	700.1	700.8
162.5°	709.0	709.8	710.5	711.2	711.6	711.2	710.3	709.5	708.6	707.8	708.6
165°	716.5	717.5	718.4	719.4	719.9	719.3	718.2	717.1	716.0	714.9	716.0
167.5°	722.1	723.2	724.3	725.4	725.9	725.3	724.1	722.8	721.6	720.4	721.6
170°	727.5	728.5	729.4	730.4	730.9	730.3	729.1	727.8	726.6	725.4	726.6
172.5°	730.8	731.8	732.7	733.7	734.2	733.5	732.2	730.8	729.5	728.1	729.5
175°	733.1	734.2	735.3	736.4	736.9	736.2	734.7	733.2	731.8	730.3	731.8
177.5°	734.6	735.6	736.5	737.5	738.0	737.3	735.8	734.3	732.9	731.4	732.9
180°	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9
2.5°	591.1	588.0	587.5	587.5	582.7	585.3	580.0	574.2	571.6	571.6	566.7
5°	640.3	637.2	634.1	629.2	629.2	626.5	618.1	609.7	603.5	598.2	592.4
7.5°	690.8	687.7	678.8	673.9	676.6	671.3	660.2	646.0	635.4	627.0	615.0
10°	745.7	737.3	732.9	730.2	720.9	715.1	702.3	681.5	668.2	657.1	641.6
12.5°	790.5	793.1	776.3	777.6	768.3	760.3	740.4	720.5	700.5	685.0	662.0
15°	838.8	830.8	820.6	812.6	809.5	799.8	782.9	756.3	734.6	710.3	684.1
17.5°	876.9	870.7	860.9	853.4	846.7	823.3	809.1	785.6	755.9	732.0	700.1
20°	909.2	903.4	889.7	884.8	872.9	856.0	835.7	799.3	772.7	746.6	715.6
22.5°	922.9	917.2	905.2	899.0	891.5	875.1	855.6	821.0	788.2	755.5	722.7
25°	911.4	911.4	905.7	903.4	896.8	882.2	862.2	833.0	798.0	762.5	723.6
27.5°	855.6	866.7	870.7	872.9	872.9	873.3	859.6	831.2	797.1	762.5	721.8
30°	775.0	793.6	810.0	814.8	823.3	832.6	838.3	824.6	794.0	757.7	716.9
32.5°	673.5	697.4	728.0	735.5	747.0	775.0	790.5	796.2	779.4	747.5	704.1
35°	572.5	602.6	621.2	644.2	654.9	696.1	730.6	751.5	747.5	728.4	689.0
37.5°	484.3	501.6	524.2	548.5	569.8	609.2	652.2	692.5	708.9	699.6	669.9
40°	399.7	420.0	447.1	467.0	481.6	521.1	574.2	618.1	654.0	659.8	641.6
42.5°	339.8	360.2	376.6	398.3	409.9	448.0	494.9	549.9	592.4	615.0	607.0
45°	293.8	306.2	319.5	331.9	346.0	379.7	423.1	483.4	531.3	563.2	566.3
47.5°	253.4	264.5	276.0	287.6	295.5	321.7	361.6	410.7	463.0	506.9	524.2
50°	225.1	230.4	238.8	245.5	254.8	277.4	309.3	351.8	407.2	454.6	477.2
52.5°	197.2	203.8	210.5	216.2	222.4	238.4	267.6	304.4	352.3	401.0	428.9
55°	173.7	179.0	185.2	189.2	192.7	206.9	229.1	257.4	298.6	344.7	379.3
57.5°	154.6	156.9	162.2	164.4	168.4	179.9	195.8	221.1	254.3	299.1	327.4
60°	133.8	138.2	142.2	144.0	147.1	155.1	166.2	189.6	218.4	251.2	283.6
62.5°	117.0	118.7	121.8	124.1	126.3	134.7	144.0	161.7	183.4	210.9	240.6
65°	101.5	102.4	104.1	107.2	108.6	114.8	120.1	132.9	153.3	174.1	203.8
67.5°	85.5	86.4	88.6	90.4	91.7	95.7	101.5	110.8	121.8	144.9	161.3
70°	73.1	73.1	74.4	75.3	76.7	78.4	81.5	88.6	98.8	113.4	128.5
72.5°	61.1	61.1	61.1	62.5	62.5	63.8	65.6	70.5	77.5	89.1	98.8
75°	47.4	47.9	48.7	48.7	49.2	51.0	52.3	53.6	57.2	64.7	73.6
77.5°	35.9	36.8	37.2	36.3	37.2	37.2	39.0	40.8	42.5	44.8	51.4
80°	26.6	27.0	26.1	26.6	26.6	27.5	28.4	27.9	28.8	31.5	33.2
82.5°	17.7	18.2	18.2	18.2	18.2	19.5	19.5	19.1	19.5	19.9	20.4
85°	11.1	10.6	10.6	11.1	10.6	10.6	11.1	11.5	11.1	11.5	12.0
87.5°	4.9	4.9	4.9	4.9	4.4	4.4	4.9	4.4	4.9	4.4	4.0
90°	16.0	15.8	15.5	15.4	15.0	14.3	13.6	12.8	12.1	11.1	10.1
92.5°	14.8	14.8	14.8	14.8	14.4	13.7	13.0	12.2	11.5	10.5	9.5
95°	15.7	15.6	15.5	15.4	15.0	14.3	13.6	12.8	12.1	12.0	11.8
97.5°	15.1	15.0	14.9	14.8	14.5	13.9	13.3	12.7	12.1	24.9	37.7
100°	15.1	15.0	14.9	14.8	15.8	17.9	20.0	22.1	24.2	41.0	57.9
102.5°	15.9	15.9	15.9	15.9	29.6	57.1	84.6	112.1	139.6	138.1	136.7
105°	165.4	169.8	174.2	176.4	175.9	174.8	173.7	172.6	171.5	170.9	170.3
107.5°	210.6	210.1	209.6	209.4	209.1	208.5	207.8	207.2	206.6	205.8	204.9
110°	244.3	244.0	243.6	243.4	243.3	243.0	242.8	242.5	242.3	241.6	240.8

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	277.6	277.1	276.6	276.4	276.5	276.6	276.7	276.9	277.0	276.8	276.5
115°	311.0	311.0	311.0	311.0	310.9	310.6	310.4	310.1	309.9	310.0	310.2
117.5°	344.6	344.6	344.6	344.6	344.7	344.8	344.9	345.0	345.1	344.7	344.4
120°	376.4	376.6	376.9	377.0	376.9	376.6	376.4	376.1	375.9	376.0	376.1
122.5°	407.2	407.4	407.7	407.8	407.7	407.6	407.5	407.3	407.2	407.0	406.7
125°	437.2	437.1	437.0	436.9	436.7	436.3	436.0	435.6	435.2	435.4	435.7
127.5°	464.6	464.7	464.8	464.9	465.0	465.1	465.2	465.4	465.5	464.9	464.3
130°	491.8	491.8	491.8	491.8	491.7	491.6	491.5	491.4	491.3	490.9	490.5
132.5°	517.4	517.5	517.6	517.7	517.6	517.5	517.4	517.2	517.1	516.6	516.1
135°	541.9	541.7	541.4	541.3	541.2	540.9	540.7	540.4	540.2	539.7	539.2
137.5°	564.1	564.2	564.3	564.4	564.3	564.0	563.8	563.5	563.3	562.7	562.1
140°	586.1	586.0	585.9	585.8	585.6	585.2	584.9	584.5	584.1	583.9	583.7
142.5°	605.0	605.0	605.0	605.0	604.9	604.6	604.4	604.1	603.9	603.8	603.7
145°	623.8	623.6	623.3	623.2	623.1	623.0	622.9	622.7	622.6	622.6	622.6
147.5°	640.0	639.9	639.8	639.7	639.6	639.5	639.4	639.2	639.1	639.2	639.4
150°	655.3	655.2	655.1	655.0	655.0	655.0	655.0	655.0	655.0	655.1	655.3
152.5°	669.0	669.1	669.2	669.3	669.2	668.9	668.7	668.4	668.2	668.4	668.7
155°	681.1	681.4	681.8	682.0	681.8	681.3	680.8	680.3	679.8	680.2	680.5
157.5°	691.4	692.1	692.7	693.0	692.7	692.1	691.4	690.8	690.2	690.7	691.2
160°	701.6	702.3	703.0	703.4	703.0	702.3	701.6	700.8	700.1	700.2	700.3
162.5°	709.5	710.3	711.2	711.6	711.2	710.5	709.8	709.0	708.3	708.4	708.6
165°	717.1	718.2	719.3	719.9	719.4	718.4	717.5	716.5	715.5	715.5	715.5
167.5°	722.8	724.1	725.3	725.9	725.4	724.3	723.2	722.1	721.0	721.1	721.2
170°	727.8	729.1	730.3	730.9	730.4	729.4	728.5	727.5	726.5	726.4	726.2
172.5°	730.8	732.2	733.5	734.2	733.7	732.7	731.8	730.8	729.8	729.7	729.5
175°	733.2	734.7	736.2	736.9	736.4	735.3	734.2	733.1	732.0	731.9	731.7
177.5°	734.3	735.8	737.3	738.0	737.5	736.5	735.6	734.6	733.6	733.4	733.1
180°	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9
2.5°	564.0	561.8	560.5	560.1	556.1	553.9	552.5	551.6	550.3	546.8	543.7
5°	585.3	579.1	576.0	572.5	566.3	559.2	553.4	549.9	545.4	538.3	531.7
7.5°	605.3	595.9	589.7	584.9	574.2	562.7	553.4	545.9	537.5	527.7	518.4
10°	626.1	611.0	603.0	595.5	580.0	564.9	551.6	540.6	528.6	515.7	505.6
12.5°	642.5	622.5	613.7	603.0	584.0	566.3	549.4	534.4	518.9	505.1	490.5
15°	661.5	636.7	626.5	612.8	586.6	563.6	541.9	525.5	509.5	489.2	473.7
17.5°	672.6	643.8	629.2	617.2	588.9	560.9	535.7	515.3	496.7	476.3	459.9
20°	683.7	650.9	634.5	617.7	584.0	554.3	527.7	503.3	483.8	461.7	444.9
22.5°	687.2	649.1	631.8	616.3	580.9	547.7	517.1	492.3	469.7	447.5	428.5
25°	687.2	648.7	628.3	608.4	571.1	537.0	506.4	479.4	454.2	432.0	413.0
27.5°	680.1	639.8	618.5	600.4	561.8	525.1	493.6	463.9	439.5	417.4	395.7
30°	671.3	627.0	605.7	584.0	546.8	511.8	477.6	450.2	424.5	399.2	379.7
32.5°	660.2	613.2	589.7	567.6	528.2	491.8	460.4	433.3	409.0	382.8	361.1
35°	644.2	592.8	566.7	547.2	509.1	471.4	441.3	414.7	391.2	364.2	340.7
37.5°	623.9	574.2	547.7	523.7	484.3	449.7	421.4	395.7	372.6	347.8	321.7
40°	599.9	548.1	525.1	499.8	458.1	425.4	398.8	375.7	352.7	329.2	304.0
42.5°	572.9	521.5	495.8	471.4	431.6	399.2	374.4	353.6	332.3	310.6	283.6
45°	540.6	492.3	467.5	444.4	405.9	372.6	350.0	330.1	311.9	289.8	265.9
47.5°	504.2	462.1	436.9	412.1	374.4	345.6	323.5	306.6	291.1	269.0	247.2
50°	468.8	427.1	406.8	381.5	346.9	319.9	297.3	283.1	271.2	249.5	230.0
52.5°	424.0	392.6	373.1	351.4	318.1	290.7	272.9	260.5	246.4	229.5	212.2
55°	384.6	355.4	339.8	319.5	286.7	262.3	247.2	235.7	224.6	209.6	195.8
57.5°	339.8	321.7	306.2	288.4	256.1	235.3	222.0	212.2	202.0	189.6	178.6
60°	292.9	284.5	269.4	255.2	227.7	209.6	198.5	189.6	179.9	169.7	160.4
62.5°	251.2	246.4	237.5	226.4	200.7	185.2	174.1	167.5	160.4	151.1	142.2
65°	211.8	209.6	201.2	193.2	175.5	161.7	152.0	148.0	140.0	132.9	124.9
67.5°	176.8	174.1	169.3	165.7	150.6	137.8	132.9	127.6	121.0	115.6	109.0
70°	141.3	140.9	137.8	133.4	125.4	116.1	111.2	107.7	101.0	97.0	92.2
72.5°	109.9	112.1	109.4	107.7	102.4	95.7	91.3	89.1	83.7	80.6	77.1
75°	82.0	83.7	85.1	82.0	80.6	77.5	73.6	71.3	68.7	64.2	62.9
77.5°	55.8	59.8	59.8	60.7	61.1	59.4	56.3	54.5	51.4	50.5	48.7
80°	36.8	40.3	40.8	41.6	43.0	43.0	40.8	40.3	37.2	36.8	35.4
82.5°	21.3	24.4	26.1	27.5	27.0	28.8	27.0	26.6	24.8	24.8	23.9
85°	11.5	12.0	12.8	13.7	14.6	15.5	15.5	15.1	14.6	14.2	13.3
87.5°	4.4	4.4	4.9	4.4	4.9	5.8	6.2	6.2	5.8	5.3	4.4
90°	9.2	8.2	7.7	7.0	5.7	4.3	3.0	1.6	3.0	4.3	5.7
92.5°	8.6	7.6	7.1	7.2	7.5	7.7	8.0	8.2	8.0	7.7	7.5
95°	11.7	11.6	11.5	13.6	17.7	21.9	26.0	30.2	26.0	21.9	17.7
97.5°	50.6	63.4	69.8	68.5	65.8	63.1	60.4	57.7	60.4	63.1	65.8
100°	74.7	91.6	100.0	98.9	96.7	94.5	92.3	90.1	92.3	94.5	96.7
102.5°	135.2	133.7	133.0	132.3	130.8	129.3	127.9	126.4	127.9	129.3	130.8
105°	169.6	169.0	168.7	168.3	167.6	166.9	166.1	165.4	166.1	166.9	167.6
107.5°	204.1	203.2	202.8	202.6	202.2	201.9	201.5	201.1	201.5	201.9	202.2
110°	240.1	239.4	239.0	238.8	238.5	238.1	237.8	237.4	237.8	238.1	238.5

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	276.3	276.0	275.9	275.5	274.8	274.1	273.3	272.6	273.3	274.1	274.8
115°	310.3	310.4	310.5	310.3	309.9	309.6	309.2	308.8	309.2	309.6	309.9
117.5°	344.0	343.7	343.5	343.3	342.8	342.3	341.8	341.3	341.8	342.3	342.8
120°	376.2	376.3	376.4	376.2	375.7	375.2	374.7	374.2	374.7	375.2	375.7
122.5°	406.5	406.2	406.1	406.0	405.7	405.5	405.2	405.0	405.2	405.5	405.7
125°	435.9	436.2	436.3	436.1	435.6	435.1	434.6	434.1	434.6	435.1	435.6
127.5°	463.6	463.0	462.7	462.6	462.5	462.4	462.3	462.2	462.3	462.4	462.5
130°	490.2	489.8	489.6	489.5	489.4	489.3	489.2	489.1	489.2	489.3	489.4
132.5°	515.6	515.1	514.9	514.8	514.5	514.3	514.0	513.8	514.0	514.3	514.5
135°	538.7	538.2	538.0	538.1	538.2	538.3	538.4	538.5	538.4	538.3	538.2
137.5°	561.4	560.8	560.5	560.5	560.5	560.5	560.5	560.5	560.5	560.5	560.5
140°	583.4	583.2	583.1	583.0	582.7	582.5	582.2	582.0	582.2	582.5	582.7
142.5°	603.6	603.5	603.4	603.2	602.7	602.2	601.7	601.2	601.7	602.2	602.7
145°	622.6	622.6	622.6	622.4	622.1	621.7	621.4	621.0	621.4	621.7	622.1
147.5°	639.5	639.6	639.7	639.3	638.6	637.9	637.1	636.4	637.1	637.9	638.6
150°	655.4	655.5	655.6	655.4	654.9	654.4	653.9	653.4	653.9	654.4	654.9
152.5°	668.9	669.2	669.3	669.1	668.8	668.4	668.1	667.7	668.1	668.4	668.8
155°	680.9	681.2	681.4	681.3	681.2	681.1	681.0	680.9	681.0	681.1	681.2
157.5°	691.7	692.2	692.4	692.4	692.4	692.4	692.4	692.4	692.4	692.4	692.4
160°	700.4	700.5	700.6	700.8	701.2	701.5	701.9	702.3	701.9	701.5	701.2
162.5°	708.7	708.8	708.9	709.1	709.6	710.1	710.6	711.1	710.6	710.1	709.6
165°	715.5	715.5	715.5	715.8	716.4	717.0	717.6	718.2	717.6	717.0	716.4
167.5°	721.3	721.4	721.5	721.8	722.4	723.1	723.7	724.3	723.7	723.1	722.4
170°	726.1	726.0	725.9	726.3	727.0	727.7	728.5	729.2	728.5	727.7	727.0
172.5°	729.4	729.3	729.2	729.6	730.3	731.0	731.8	732.5	731.8	731.0	730.3
175°	731.6	731.5	731.4	731.8	732.5	733.2	734.0	734.7	734.0	733.2	732.5
177.5°	732.9	732.6	732.5	732.9	733.8	734.7	735.5	736.4	735.5	734.7	733.8
180°	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9
2.5°	541.0	540.1	539.2	535.7	532.6	527.3	522.8	521.1	520.6	521.1	519.7
5°	525.5	525.1	522.0	515.7	510.0	503.8	499.4	494.9	492.3	492.3	489.2
7.5°	510.9	507.8	505.1	497.1	490.5	482.1	475.4	471.4	469.2	464.4	464.4
10°	495.4	490.9	487.4	479.9	470.1	461.7	453.3	448.4	444.4	440.9	439.5
12.5°	479.9	476.3	469.7	461.7	451.9	441.3	432.5	428.9	419.6	412.1	412.5
15°	465.2	457.3	454.2	442.6	431.1	420.9	408.1	397.9	390.4	385.5	379.3
17.5°	448.8	440.9	435.1	425.4	410.3	394.3	381.9	368.2	360.7	352.3	348.3
20°	430.7	424.0	419.6	404.1	385.9	366.9	353.1	344.7	336.3	330.1	326.6
22.5°	415.2	406.8	401.4	380.6	360.7	341.6	331.0	323.9	316.8	311.5	309.7
25°	395.2	390.4	377.5	359.3	335.0	322.1	312.8	303.5	299.5	296.0	292.0
27.5°	378.8	366.9	358.0	334.1	319.0	304.4	295.1	288.0	283.1	279.6	276.5
30°	358.5	347.4	335.0	315.0	301.3	287.6	279.1	273.4	268.1	265.9	263.2
32.5°	337.2	327.0	315.0	299.1	282.2	271.6	265.0	258.8	255.2	253.0	249.9
35°	318.1	305.3	297.3	282.2	268.5	256.5	250.3	245.0	241.0	240.2	239.7
37.5°	297.8	288.0	280.5	265.0	253.4	243.3	237.5	231.7	229.5	229.1	227.3
40°	280.0	271.6	264.5	249.9	237.5	228.2	223.8	220.2	218.0	218.0	217.6
42.5°	264.5	255.7	248.6	235.3	224.2	215.8	210.9	207.4	206.5	206.9	206.5
45°	247.2	239.7	232.6	218.9	209.6	203.4	198.1	196.3	195.0	195.4	195.8
47.5°	230.8	224.6	217.6	206.5	195.8	189.2	186.1	184.3	184.3	184.3	185.2
50°	216.2	209.1	202.9	191.4	181.7	176.3	173.7	171.5	171.9	172.4	172.8
52.5°	198.9	192.7	188.3	176.8	169.7	163.1	160.0	160.4	160.0	160.0	160.8
55°	183.9	177.7	173.2	162.6	155.5	151.1	148.4	147.1	147.5	146.7	148.4
57.5°	167.0	161.7	158.6	148.4	142.2	138.2	136.0	133.8	134.7	134.3	133.8
60°	152.4	146.2	141.3	134.3	128.9	124.1	122.7	120.5	121.4	120.5	120.1
62.5°	135.6	130.7	127.2	120.1	115.6	111.7	108.6	107.2	106.8	105.5	104.1
65°	118.7	116.1	112.5	105.5	101.0	97.9	96.1	94.8	94.4	90.8	86.8
67.5°	103.2	101.5	97.9	92.6	88.6	85.5	82.9	80.6	78.0	75.3	73.1
70°	88.6	86.0	83.7	78.9	75.3	72.2	69.6	66.9	65.6	62.9	62.0
72.5°	74.4	71.8	69.6	65.1	62.0	58.9	58.0	54.9	53.6	53.2	53.2
75°	59.8	57.6	56.3	52.3	49.6	47.4	46.1	45.2	44.3	43.4	42.1
77.5°	45.6	44.3	43.4	40.8	38.5	37.2	36.8	33.7	32.8	31.9	31.0
80°	33.2	32.8	31.9	29.7	28.8	25.7	25.7	24.8	24.4	24.4	24.4
82.5°	22.6	21.7	21.3	19.1	18.6	18.2	17.7	17.3	17.7	17.3	17.7
85°	12.0	11.5	11.1	11.1	11.1	11.1	11.1	11.1	11.1	10.6	11.1
87.5°	4.4	4.4	4.4	4.4	4.0	4.4	4.4	4.0	4.4	4.4	4.4
90°	7.0	7.7	8.2	9.2	10.1	11.1	12.1	12.8	13.6	14.3	15.0
92.5°	7.2	7.1	7.6	8.6	9.5	10.5	11.5	12.2	13.0	13.7	14.4
95°	13.6	11.5	11.6	11.7	11.8	12.0	12.1	12.8	13.6	14.3	15.0
97.5°	68.5	69.8	63.4	50.6	37.7	24.9	12.1	12.7	13.3	13.9	14.5
100°	98.9	100.0	91.6	74.7	57.9	41.0	24.2	22.1	20.0	17.9	15.8
102.5°	132.3	133.0	133.7	135.2	136.7	138.1	139.6	112.1	84.6	57.1	29.6
105°	168.3	168.7	169.0	169.6	170.3	170.9	171.5	172.6	173.7	174.8	175.9
107.5°	202.6	202.8	203.2	204.1	204.9	205.8	206.6	207.2	207.8	208.5	209.1
110°	238.8	239.0	239.4	240.1	240.8	241.6	242.3	242.5	242.8	243.0	243.3

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	275.5	275.9	276.0	276.3	276.5	276.8	277.0	276.9	276.7	276.6	276.5
115°	310.3	310.5	310.4	310.3	310.2	310.0	309.9	310.1	310.4	310.6	310.9
117.5°	343.3	343.5	343.7	344.0	344.4	344.7	345.1	345.0	344.9	344.8	344.7
120°	376.2	376.4	376.3	376.2	376.1	376.0	375.9	376.1	376.4	376.6	376.9
122.5°	406.0	406.1	406.2	406.5	406.7	407.0	407.2	407.3	407.5	407.6	407.7
125°	436.1	436.3	436.2	435.9	435.7	435.4	435.2	435.6	436.0	436.3	436.7
127.5°	462.6	462.7	463.0	463.6	464.3	464.9	465.5	465.4	465.2	465.1	465.0
130°	489.5	489.6	489.8	490.2	490.5	490.9	491.3	491.4	491.5	491.6	491.7
132.5°	514.8	514.9	515.1	515.6	516.1	516.6	517.1	517.2	517.4	517.5	517.6
135°	538.1	538.0	538.2	538.7	539.2	539.7	540.2	540.4	540.7	540.9	541.2
137.5°	560.5	560.5	560.8	561.4	562.1	562.7	563.3	563.5	563.8	564.0	564.3
140°	583.0	583.1	583.2	583.4	583.7	583.9	584.1	584.5	584.9	585.2	585.6
142.5°	603.2	603.4	603.5	603.6	603.7	603.8	603.9	604.1	604.4	604.6	604.9
145°	622.4	622.6	622.6	622.6	622.6	622.6	622.6	622.7	622.9	623.0	623.1
147.5°	639.3	639.7	639.6	639.5	639.4	639.2	639.1	639.2	639.4	639.5	639.6
150°	655.4	655.6	655.5	655.4	655.3	655.1	655.0	655.0	655.0	655.0	655.0
152.5°	669.1	669.3	669.2	668.9	668.7	668.4	668.2	668.4	668.7	668.9	669.2
155°	681.3	681.4	681.2	680.9	680.5	680.2	679.8	680.3	680.8	681.3	681.8
157.5°	692.4	692.4	692.2	691.7	691.2	690.7	690.2	690.8	691.4	692.1	692.7
160°	700.8	700.6	700.5	700.4	700.3	700.2	700.1	700.8	701.6	702.3	703.0
162.5°	709.1	708.9	708.8	708.7	708.6	708.4	708.3	709.0	709.8	710.5	711.2
165°	715.8	715.5	715.5	715.5	715.5	715.5	715.5	716.5	717.5	718.4	719.4
167.5°	721.8	721.5	721.4	721.3	721.2	721.1	721.0	722.1	723.2	724.3	725.4
170°	726.3	725.9	726.0	726.1	726.2	726.4	726.5	727.5	728.5	729.4	730.4
172.5°	729.6	729.2	729.3	729.4	729.5	729.7	729.8	730.8	731.8	732.7	733.7
175°	731.8	731.4	731.5	731.6	731.7	731.9	732.0	733.1	734.2	735.3	736.4
177.5°	732.9	732.5	732.6	732.9	733.1	733.4	733.6	734.6	735.6	736.5	737.5
180°	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9
2.5°	519.7	521.5	519.3	520.6	517.5	517.1	517.5	517.5	518.0	518.4	518.9
5°	490.5	490.1	487.4	485.6	484.3	485.6	486.5	487.4	486.5	487.4	487.8
7.5°	463.0	461.7	460.4	457.3	458.1	457.3	459.9	458.6	458.6	460.8	462.6
10°	438.7	436.0	435.1	431.6	428.9	428.5	431.6	432.9	434.2	435.1	438.7
12.5°	407.2	403.2	400.1	401.4	393.9	397.0	397.9	396.1	401.4	407.6	404.1
15°	373.5	374.0	367.8	365.5	359.3	361.1	361.6	366.0	370.4	370.0	375.3
17.5°	348.7	346.0	340.7	340.3	337.6	339.0	338.5	342.1	340.7	342.9	347.4
20°	325.7	323.9	319.5	317.7	318.6	317.7	318.1	318.6	319.9	324.8	323.9
22.5°	307.5	305.3	305.3	303.1	300.4	299.5	301.7	303.1	304.8	305.7	307.9
25°	291.5	289.8	287.6	286.2	284.0	284.5	285.8	287.6	288.9	290.7	292.4
27.5°	275.2	275.2	272.9	272.5	271.6	271.2	272.9	273.8	273.8	275.2	276.9
30°	262.3	262.3	260.1	259.6	259.2	259.2	260.5	261.0	261.4	262.7	263.6
32.5°	249.9	249.5	248.6	249.0	248.6	249.0	249.0	249.5	250.3	250.8	252.6
35°	238.4	238.8	237.9	237.9	237.5	237.9	238.8	239.3	239.7	240.6	240.6
37.5°	227.3	228.2	227.7	229.1	229.1	229.1	229.1	230.0	230.0	230.0	229.5
40°	217.6	217.6	217.1	218.0	218.9	218.9	219.3	219.3	219.8	219.8	219.3
42.5°	206.5	207.4	208.7	209.1	210.0	209.6	210.9	210.5	210.9	210.0	209.1
45°	196.3	196.3	198.1	199.8	200.3	200.3	200.3	201.2	200.3	198.9	198.5
47.5°	185.2	186.1	187.0	189.2	189.6	189.6	189.6	189.6	188.8	188.8	188.8
50°	174.1	174.6	175.0	175.9	177.2	176.8	176.8	176.8	178.6	176.8	177.2
52.5°	160.8	161.3	161.7	163.5	163.1	163.1	163.5	163.5	164.8	164.4	163.5
55°	147.5	147.5	148.4	148.4	148.4	149.3	149.8	150.6	150.2	150.6	151.1
57.5°	134.3	133.4	132.9	132.9	134.3	133.8	134.3	134.3	136.0	136.9	137.4
60°	118.7	118.7	118.3	115.6	115.6	115.2	116.5	117.4	118.3	122.3	121.8
62.5°	102.8	101.0	99.3	99.7	97.0	98.4	97.5	98.4	101.0	104.1	104.6
65°	86.8	85.5	83.7	83.3	82.4	83.7	83.3	83.7	85.1	86.8	89.1
67.5°	72.7	72.2	71.3	70.9	70.9	70.9	71.8	71.8	72.2	73.6	74.9
70°	62.0	61.6	62.0	61.1	61.6	61.1	61.6	62.0	62.5	62.9	64.2
72.5°	52.3	52.3	52.3	51.4	52.3	51.8	51.8	52.3	52.7	53.2	54.1
75°	41.6	40.8	39.9	39.0	38.5	39.4	39.9	39.4	40.8	42.5	42.5
77.5°	31.5	31.0	31.0	31.0	31.5	31.0	31.9	31.5	31.9	31.9	32.8
80°	24.4	23.9	24.4	24.4	23.9	24.8	24.4	24.4	24.8	25.3	24.8
82.5°	17.7	18.2	17.7	17.7	17.7	18.6	17.7	17.7	17.7	18.2	18.2
85°	11.1	11.1	11.1	11.1	11.5	11.1	11.5	11.1	12.0	11.5	11.5
87.5°	4.0	4.4	4.9	4.9	4.9	4.9	4.4	4.9	5.3	4.9	5.3
90°	15.4	15.5	15.8	16.0	16.3	16.5	16.3	16.0	15.8	15.5	15.4
92.5°	14.8	14.8	14.8	14.8	14.8	14.8	14.8	14.8	14.8	14.8	14.8
95°	15.4	15.5	15.6	15.7	15.8	15.9	15.8	15.7	15.6	15.5	15.4
97.5°	14.8	14.9	15.0	15.1	15.3	15.4	15.3	15.1	15.0	14.9	14.8
100°	14.8	14.9	15.0	15.1	15.3	15.4	15.3	15.1	15.0	14.9	14.8
102.5°	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9
105°	176.4	174.2	169.8	165.4	161.0	156.6	161.0	165.4	169.8	174.2	176.4
107.5°	209.4	209.6	210.1	210.6	211.1	211.6	211.1	210.6	210.1	209.6	209.4
110°	243.4	243.6	244.0	244.3	244.7	245.1	244.7	244.3	244.0	243.6	243.4

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	276.4	276.6	277.1	277.6	278.1	278.6	278.1	277.6	277.1	276.6	276.4
115°	311.0	311.0	311.0	311.0	311.0	311.0	311.0	311.0	311.0	311.0	311.0
117.5°	344.6	344.6	344.6	344.6	344.6	344.6	344.6	344.6	344.6	344.6	344.6
120°	377.0	376.9	376.6	376.4	376.1	375.9	376.1	376.4	376.6	376.9	377.0
122.5°	407.8	407.7	407.4	407.2	406.9	406.7	406.9	407.2	407.4	407.7	407.8
125°	436.9	437.0	437.1	437.2	437.3	437.4	437.3	437.2	437.1	437.0	436.9
127.5°	464.9	464.8	464.7	464.6	464.5	464.4	464.5	464.6	464.7	464.8	464.9
130°	491.8	491.8	491.8	491.8	491.8	491.8	491.8	491.8	491.8	491.8	491.8
132.5°	517.7	517.6	517.5	517.4	517.2	517.1	517.2	517.4	517.5	517.6	517.7
135°	541.3	541.4	541.7	541.9	542.2	542.4	542.2	541.9	541.7	541.4	541.3
137.5°	564.4	564.3	564.2	564.1	563.9	563.8	563.9	564.1	564.2	564.3	564.4
140°	585.8	585.9	586.0	586.1	586.2	586.3	586.2	586.1	586.0	585.9	585.8
142.5°	605.0	605.0	605.0	605.0	605.0	605.0	605.0	605.0	605.0	605.0	605.0
145°	623.2	623.3	623.6	623.8	624.1	624.3	624.1	623.8	623.6	623.3	623.2
147.5°	639.7	639.8	639.9	640.0	640.1	640.2	640.1	640.0	639.9	639.8	639.7
150°	655.0	655.1	655.2	655.3	655.5	655.6	655.5	655.3	655.2	655.1	655.0
152.5°	669.3	669.2	669.1	669.0	668.9	668.8	668.9	669.0	669.1	669.2	669.3
155°	682.0	681.8	681.4	681.1	680.7	680.3	680.7	681.1	681.4	681.8	682.0
157.5°	693.0	692.7	692.1	691.4	690.8	690.2	690.8	691.4	692.1	692.7	693.0
160°	703.4	703.0	702.3	701.6	700.8	700.1	700.8	701.6	702.3	703.0	703.4
162.5°	711.6	711.2	710.3	709.5	708.6	707.8	708.6	709.5	710.3	711.2	711.6
165°	719.9	719.3	718.2	717.1	716.0	714.9	716.0	717.1	718.2	719.3	719.9
167.5°	725.9	725.3	724.1	722.8	721.6	720.4	721.6	722.8	724.1	725.3	725.9
170°	730.9	730.3	729.1	727.8	726.6	725.4	726.6	727.8	729.1	730.3	730.9
172.5°	734.2	733.5	732.2	730.8	729.5	728.1	729.5	730.8	732.2	733.5	734.2
175°	736.9	736.2	734.7	733.2	731.8	730.3	731.8	733.2	734.7	736.2	736.9
177.5°	738.0	737.3	735.8	734.3	732.9	731.4	732.9	734.3	735.8	737.3	738.0
180°	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9
2.5°	520.6	522.8	522.0	518.9	520.2	522.8	525.5	529.0	531.3	533.0	533.9
5°	490.1	494.0	493.2	493.2	494.9	499.4	503.8	511.3	514.0	517.1	521.5
7.5°	463.0	466.1	468.8	469.7	472.3	478.1	483.8	492.3	498.9	502.5	505.1
10°	439.1	441.3	445.3	447.5	450.2	457.3	465.7	474.5	481.2	487.4	490.9
12.5°	408.5	417.4	422.7	426.2	429.8	440.4	447.1	456.8	464.8	470.6	475.9
15°	374.4	385.0	388.1	401.9	410.7	419.2	429.3	440.9	448.4	455.0	462.1
17.5°	345.6	353.1	356.7	371.3	378.8	392.1	406.8	421.4	432.9	437.8	444.9
20°	327.4	331.4	338.5	343.4	351.4	366.9	382.8	400.5	417.8	422.7	429.8
22.5°	308.8	314.1	319.0	325.7	331.9	342.5	358.5	378.0	396.6	405.4	413.8
25°	292.0	297.3	300.4	307.5	313.3	323.9	335.0	354.9	377.1	384.6	397.9
27.5°	278.7	281.8	287.1	290.2	296.9	306.6	316.8	331.9	353.6	366.4	379.3
30°	265.4	267.6	272.1	276.5	281.4	288.0	299.5	314.1	334.1	345.2	358.0
32.5°	252.1	255.7	258.3	261.4	266.7	274.7	282.7	296.9	312.8	325.2	338.1
35°	241.0	242.4	245.9	249.5	253.0	260.1	268.5	282.2	296.4	306.2	317.7
37.5°	229.1	231.3	233.9	235.3	241.0	245.5	254.3	265.0	281.8	288.0	299.5
40°	219.8	219.3	222.0	224.2	226.9	233.9	239.3	250.8	264.1	273.8	280.9
42.5°	208.2	208.2	209.1	211.8	215.3	219.8	226.0	235.7	249.5	256.5	265.0
45°	198.9	197.6	198.1	199.8	202.0	206.5	212.7	221.1	234.8	240.6	249.5
47.5°	187.9	186.5	186.5	188.3	190.1	193.2	198.1	207.8	218.9	226.4	233.1
50°	175.5	175.9	175.5	176.8	177.7	180.8	186.1	194.1	204.3	210.5	218.0
52.5°	163.9	163.1	162.6	163.5	165.3	167.5	173.2	180.3	190.1	196.3	202.9
55°	149.8	150.6	150.6	150.6	153.3	154.2	158.6	165.7	175.5	180.3	186.5
57.5°	136.9	136.5	137.4	136.9	139.1	142.2	145.8	151.1	160.8	165.7	171.5
60°	122.7	123.2	123.6	123.6	125.4	128.5	132.5	137.4	145.3	150.2	155.5
62.5°	105.5	107.7	109.9	110.8	113.4	115.6	118.3	123.6	130.7	134.3	139.1
65°	89.1	92.2	95.3	97.5	99.3	101.5	105.0	109.9	115.6	119.2	124.1
67.5°	74.9	77.1	81.1	83.3	86.8	89.5	91.7	95.7	102.8	104.1	108.1
70°	64.7	65.6	67.3	69.1	73.1	75.3	78.0	82.0	87.3	90.4	92.6
72.5°	54.5	54.9	55.8	57.6	59.4	62.0	65.1	68.7	73.6	74.9	78.0
75°	43.4	46.1	46.1	47.4	48.7	50.1	52.7	56.3	59.4	61.6	63.4
77.5°	32.3	33.7	34.6	36.8	38.5	39.9	41.6	44.3	46.1	47.9	49.2
80°	25.3	25.7	26.1	26.1	27.0	28.8	30.6	32.3	34.6	35.4	36.8
82.5°	18.6	18.6	18.6	19.5	19.9	20.4	20.4	21.3	23.5	24.4	25.7
85°	12.0	12.0	12.0	12.0	12.4	12.8	13.3	13.7	13.7	13.7	14.6
87.5°	4.9	5.8	5.3	5.8	5.8	5.8	5.8	6.2	6.2	6.6	6.6
90°	15.0	14.3	13.6	12.8	12.1	11.1	10.1	9.2	8.2	7.7	7.0
92.5°	14.4	13.7	13.0	12.2	11.5	10.5	9.5	8.6	7.6	7.1	7.2
95°	15.0	14.3	13.6	12.8	12.1	12.0	11.8	11.7	11.6	11.5	13.6
97.5°	14.5	13.9	13.3	12.7	12.1	24.9	37.7	50.6	63.4	69.8	68.5
100°	15.8	17.9	20.0	22.1	24.2	41.0	57.9	74.7	91.6	100.0	98.9
102.5°	29.6	57.1	84.6	112.1	139.6	138.1	136.7	135.2	133.7	133.0	132.3
105°	175.9	174.8	173.7	172.6	171.5	170.9	170.3	169.6	169.0	168.7	168.3
107.5°	209.1	208.5	207.8	207.2	206.6	205.8	204.9	204.1	203.2	202.8	202.6
110°	243.3	243.0	242.8	242.5	242.3	241.6	240.8	240.1	239.4	239.0	238.8

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	276.5	276.6	276.7	276.9	277.0	276.8	276.5	276.3	276.0	275.9	275.5
115°	310.9	310.6	310.4	310.1	309.9	310.0	310.2	310.3	310.4	310.5	310.3
117.5°	344.7	344.8	344.9	345.0	345.1	344.7	344.4	344.0	343.7	343.5	343.3
120°	376.9	376.6	376.4	376.1	375.9	376.0	376.1	376.2	376.3	376.4	376.2
122.5°	407.7	407.6	407.5	407.3	407.2	407.0	406.7	406.5	406.2	406.1	406.0
125°	436.7	436.3	436.0	435.6	435.2	435.4	435.7	435.9	436.2	436.3	436.1
127.5°	465.0	465.1	465.2	465.4	465.5	464.9	464.3	463.6	463.0	462.7	462.6
130°	491.7	491.6	491.5	491.4	491.3	490.9	490.5	490.2	489.8	489.6	489.5
132.5°	517.6	517.5	517.4	517.2	517.1	516.6	516.1	515.6	515.1	514.9	514.8
135°	541.2	540.9	540.7	540.4	540.2	539.7	539.2	538.7	538.2	538.0	538.1
137.5°	564.3	564.0	563.8	563.5	563.3	562.7	562.1	561.4	560.8	560.5	560.5
140°	585.6	585.2	584.9	584.5	584.1	583.9	583.7	583.4	583.2	583.1	583.0
142.5°	604.9	604.6	604.4	604.1	603.9	603.8	603.7	603.6	603.5	603.4	603.2
145°	623.1	623.0	622.9	622.7	622.6	622.6	622.6	622.6	622.6	622.6	622.4
147.5°	639.6	639.5	639.4	639.2	639.1	639.2	639.4	639.5	639.6	639.7	639.3
150°	655.0	655.0	655.0	655.0	655.0	655.1	655.3	655.4	655.5	655.6	655.4
152.5°	669.2	668.9	668.7	668.4	668.2	668.4	668.7	668.9	669.2	669.3	669.1
155°	681.8	681.3	680.8	680.3	679.8	680.2	680.5	680.9	681.2	681.4	681.3
157.5°	692.7	692.1	691.4	690.8	690.2	690.7	691.2	691.7	692.2	692.4	692.4
160°	703.0	702.3	701.6	700.8	700.1	700.2	700.3	700.4	700.5	700.6	700.8
162.5°	711.2	710.5	709.8	709.0	708.3	708.4	708.6	708.7	708.8	708.9	709.1
165°	719.4	718.4	717.5	716.5	715.5	715.5	715.5	715.5	715.5	715.5	715.8
167.5°	725.4	724.3	723.2	722.1	721.0	721.1	721.2	721.3	721.4	721.5	721.8
170°	730.4	729.4	728.5	727.5	726.5	726.4	726.2	726.1	726.0	725.9	726.3
172.5°	733.7	732.7	731.8	730.8	729.8	729.7	729.5	729.4	729.3	729.2	729.6
175°	736.4	735.3	734.2	733.1	732.0	731.9	731.7	731.6	731.5	731.4	731.8
177.5°	737.5	736.5	735.6	734.6	733.6	733.4	733.1	732.9	732.6	732.5	732.9
180°	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	549.9	549.9	549.9	549.9
2.5°	537.5	540.1	544.6	550.8
5°	525.1	532.6	539.7	549.0
7.5°	514.0	522.8	532.6	545.9
10°	501.1	512.2	524.6	541.0
12.5°	486.1	501.6	515.7	533.5
15°	475.0	486.5	504.7	525.5
17.5°	459.5	475.0	493.2	516.6
20°	444.9	461.3	481.6	506.0
22.5°	429.3	448.0	468.3	494.5
25°	413.4	433.3	453.7	481.6
27.5°	398.8	416.9	440.0	468.3
30°	381.1	401.9	424.0	453.7
32.5°	363.8	385.5	408.1	437.8
35°	345.2	366.9	391.7	420.0
37.5°	327.0	350.9	373.5	401.0
40°	307.1	331.9	355.4	383.3
42.5°	287.6	313.3	336.7	360.7
45°	269.4	294.7	315.9	338.5
47.5°	252.1	274.7	296.4	316.8
50°	235.3	254.3	274.3	291.1
52.5°	217.6	235.7	251.7	266.7
55°	201.6	215.8	230.0	243.7
57.5°	182.6	196.7	209.1	219.8
60°	166.6	175.5	187.4	198.5
62.5°	148.4	158.6	167.9	175.0
65°	130.7	139.6	146.7	152.9
67.5°	115.6	121.0	126.3	132.9
70°	97.5	101.9	108.1	113.0
72.5°	82.0	85.5	88.6	94.4
75°	66.5	69.6	71.3	76.7
77.5°	51.4	54.5	55.8	58.9
80°	39.4	39.9	41.6	44.3
82.5°	27.0	27.9	28.4	30.6
85°	15.5	17.7	17.3	18.2
87.5°	6.6	7.1	8.0	8.9
90°	5.7	4.3	3.0	1.6
92.5°	7.5	7.7	8.0	8.2
95°	17.7	21.9	26.0	30.2
97.5°	65.8	63.1	60.4	57.7
100°	96.7	94.5	92.3	90.1
102.5°	130.8	129.3	127.9	126.4
105°	167.6	166.9	166.1	165.4
107.5°	202.2	201.9	201.5	201.1
110°	238.5	238.1	237.8	237.4

TEST NUMBER: P1013332

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	274.8	274.1	273.3	272.6
115°	309.9	309.6	309.2	308.8
117.5°	342.8	342.3	341.8	341.3
120°	375.7	375.2	374.7	374.2
122.5°	405.7	405.5	405.2	405.0
125°	435.6	435.1	434.6	434.1
127.5°	462.5	462.4	462.3	462.2
130°	489.4	489.3	489.2	489.1
132.5°	514.5	514.3	514.0	513.8
135°	538.2	538.3	538.4	538.5
137.5°	560.5	560.5	560.5	560.5
140°	582.7	582.5	582.2	582.0
142.5°	602.7	602.2	601.7	601.2
145°	622.1	621.7	621.4	621.0
147.5°	638.6	637.9	637.1	636.4
150°	654.9	654.4	653.9	653.4
152.5°	668.8	668.4	668.1	667.7
155°	681.2	681.1	681.0	680.9
157.5°	692.4	692.4	692.4	692.4
160°	701.2	701.5	701.9	702.3
162.5°	709.6	710.1	710.6	711.1
165°	716.4	717.0	717.6	718.2
167.5°	722.4	723.1	723.7	724.3
170°	727.0	727.7	728.5	729.2
172.5°	730.3	731.0	731.8	732.5
175°	732.5	733.2	734.0	734.7
177.5°	733.8	734.7	735.5	736.4
180°	734.7	734.7	734.7	734.7

(END OF REPORT)