

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013339

Luminaire Tested: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013339
REPORT IS A COMBINATION OF REPORTS P999386 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4606.0 lumens
Efficiency: N/A
Efficacy: 135.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	34	34	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	29	29	29	23
3	78	69	62	57	70	63	57	52	50	46	43	39	36	33	28	26	25	25	25	25	20
4	72	61	54	48	64	56	49	44	45	40	36	34	31	29	25	23	21	21	21	21	17
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	20	19	19	19	19	15
6	61	49	41	36	54	45	38	33	36	31	27	28	25	22	21	18	17	17	17	17	13
7	56	44	37	31	50	40	34	29	33	28	24	25	22	19	19	17	15	15	15	15	12
8	52	40	33	28	47	36	30	26	30	25	21	23	20	17	17	15	13	13	13	13	11
9	48	37	29	24	43	33	27	23	27	22	19	21	18	16	16	14	12	12	12	12	10
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	11	11	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4661	4661	4661	4661
5°	4661	5267	4669	4025
10°	4636	6072	4633	3501
15°	4581	6834	4581	2931
20°	4523	7409	4500	2582
25°	4453	7440	4433	2331
30°	4378	6327	4344	2160
35°	4272	4774	4218	2032
40°	4154	3459	4072	1931
45°	3959	2629	3861	1843
50°	3728	2125	3626	1713
55°	3477	1759	3363	1540
60°	3226	1488	3081	1281
65°	2910	1212	2817	1019
70°	2621	982	2496	827
75°	2297	708	2138	606
80°	1896	470	1723	446
85°	1375	241	1142	241

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 5835 cd/sqm

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.4	1.2
10°-20°	167.2	3.6
20°-30°	261.8	5.7
30°-40°	290.8	6.3
40°-50°	257.6	5.6
50°-60°	200.8	4.4
60°-70°	131.3	2.9
70°-80°	64.4	1.4
80°-90°	17.8	0.4
90°-100°	33.9	0.7
100°-110°	223.1	4.8
110°-120°	426.1	9.3
120°-130°	541.0	11.7
130°-140°	578.7	12.6
140°-150°	541.2	11.7
150°-160°	436.4	9.5
160°-170°	281.4	6.1
170°-180°	97.0	2.1
0°-30°	484.3	10.5
0°-40°	775.1	16.8
0°-60°	1233.5	26.8
0°-90°	1447.1	31.4
90°-120°	683.2	14.8
90°-150°	2344.0	50.9
90°-180°	3159.0	68.6
0°-180°	4606.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	572	572	572	572	572	
5°	571	660	572	505	571	54
15°	546	875	546	375	546	154
25°	501	944	498	296	501	231
35°	437	581	431	247	437	273
45°	352	297	343	208	352	271
55°	253	177	245	155	253	227
65°	159	104	154	87	159	158
75°	80	48	74	41	80	85
85°	19	12	16	12	19	21
90°	2	23	2	23	2	3
95°	42	22	42	22	42	52
105°	230	218	230	218	230	241
115°	429	432	429	432	429	422
125°	603	608	603	608	603	539
135°	748	754	748	754	748	577
145°	863	867	863	867	863	539
155°	946	945	946	945	946	436
165°	998	993	998	993	998	282
175°	1021	1015	1021	1015	1021	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	572.5	577.6	580.4	582.7	587.3	589.1	592.8	593.7	597.4	597.0	595.6
5°	570.7	579.5	585.9	592.8	601.1	605.7	610.8	618.1	621.8	626.9	630.1
7.5°	567.5	579.5	590.0	600.6	614.0	621.4	627.8	639.3	649.0	657.3	666.5
10°	562.4	577.6	593.3	607.6	626.0	634.7	644.4	661.4	674.8	686.3	701.1
12.5°	554.6	575.8	593.3	612.6	636.1	648.1	661.0	681.3	696.9	715.8	734.2
15°	546.3	569.8	592.8	618.1	644.9	658.7	671.6	698.8	722.7	744.4	764.6
17.5°	537.1	562.9	588.2	616.3	648.5	665.6	680.8	713.5	739.7	767.8	788.1
20°	526.0	554.1	583.1	614.5	650.9	669.7	686.8	724.1	753.1	783.5	808.8
22.5°	514.0	544.4	576.2	610.3	648.1	668.8	688.6	728.7	762.3	790.4	824.5
25°	500.7	532.9	565.6	601.6	643.9	666.5	686.8	726.4	762.3	799.2	832.3
27.5°	486.9	520.0	554.1	591.9	635.2	657.3	680.3	718.6	760.5	800.6	834.2
30°	471.7	503.9	539.8	575.8	621.8	643.9	667.4	708.9	754.5	794.6	831.0
32.5°	455.1	488.3	522.3	559.6	604.8	628.7	650.4	697.4	743.9	783.5	817.6
35°	436.7	468.0	500.2	538.5	583.1	604.8	630.6	679.4	726.4	768.3	790.4
37.5°	416.9	446.8	476.7	514.5	557.3	583.6	608.9	658.2	708.0	736.1	747.6
40°	398.4	424.7	450.9	487.3	530.6	557.8	583.6	634.7	678.5	700.1	691.4
42.5°	374.9	402.1	425.6	459.2	503.0	528.3	554.6	607.6	643.0	651.8	630.1
45°	351.9	374.5	397.1	429.8	475.8	497.5	525.6	574.8	604.3	596.5	564.7
47.5°	329.3	347.8	369.0	400.7	442.2	468.0	494.2	537.1	557.8	546.8	502.5
50°	302.6	321.0	343.2	370.8	410.9	435.7	456.5	496.1	511.7	484.6	431.1
52.5°	277.3	293.4	312.3	338.1	376.3	398.9	421.5	455.5	460.6	429.3	373.1
55°	253.3	266.2	286.0	306.8	341.8	365.7	381.4	410.4	409.0	369.9	321.5
57.5°	228.5	240.4	253.8	275.4	308.6	326.6	343.6	369.0	355.6	322.4	274.5
60°	206.4	213.3	226.6	247.4	275.4	291.1	304.5	318.3	306.8	270.8	234.0
62.5°	181.9	189.8	199.4	216.0	240.9	255.6	265.3	271.3	259.3	231.7	198.1
65°	158.9	165.8	176.0	190.7	209.6	220.6	225.7	229.8	223.4	192.1	165.4
67.5°	138.2	142.8	152.0	161.7	181.9	184.7	191.6	193.5	180.6	156.6	135.4
70°	117.5	122.1	126.2	137.7	146.9	152.0	153.4	153.4	140.5	124.8	107.3
72.5°	98.1	100.9	105.0	112.9	117.9	121.6	123.4	121.1	109.2	96.3	83.4
75°	79.7	81.1	84.8	89.8	94.0	92.6	92.1	89.4	80.6	71.4	64.0
77.5°	61.3	62.2	66.3	67.7	67.7	69.1	67.2	64.5	57.1	50.2	47.0
80°	46.1	47.4	47.9	48.8	47.9	47.9	46.5	41.9	38.2	35.0	32.7
82.5°	31.8	32.7	33.2	31.8	32.7	31.3	29.0	25.8	23.5	23.0	22.1
85°	18.9	19.3	18.9	18.9	17.5	17.0	15.2	14.7	13.8	13.8	13.4
87.5°	9.2	8.8	7.8	6.9	6.9	6.4	6.9	6.0	6.9	6.4	6.0
90°	2.3	4.2	6.0	7.9	9.8	10.7	11.4	12.7	14.1	15.4	16.8
92.5°	11.5	11.1	10.8	10.4	10.1	9.9	10.6	11.9	13.3	14.6	16.0
95°	42.0	36.2	30.4	24.7	18.9	16.0	16.1	16.3	16.4	16.6	16.8
97.5°	80.2	83.9	87.7	91.4	95.1	97.0	88.1	70.3	52.4	34.6	16.8
100°	125.2	128.3	131.3	134.4	137.5	139.0	127.3	103.9	80.4	57.0	33.6
102.5°	175.6	177.6	179.7	181.7	183.8	184.8	185.8	187.8	189.9	191.9	193.9
105°	229.8	230.8	231.8	232.9	233.9	234.4	234.8	235.7	236.5	237.4	238.2
107.5°	279.5	280.0	280.5	281.0	281.5	281.7	282.3	283.5	284.7	285.9	287.1
110°	329.9	330.4	330.9	331.4	331.9	332.1	332.6	333.6	334.7	335.7	336.7

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	378.7	379.7	380.7	381.8	382.8	383.3	383.5	383.8	384.1	384.5	384.8
115°	429.1	429.6	430.1	430.6	431.1	431.4	431.3	431.1	431.0	430.8	430.6
117.5°	474.2	474.9	475.5	476.2	476.9	477.2	477.5	478.0	478.5	479.0	479.5
120°	520.0	520.7	521.3	522.0	522.7	523.0	522.9	522.8	522.6	522.5	522.3
122.5°	562.7	563.1	563.4	563.8	564.1	564.3	564.5	564.8	565.1	565.5	565.8
125°	603.2	603.9	604.6	605.3	606.0	606.3	606.1	605.8	605.4	605.1	604.7
127.5°	642.1	642.3	642.5	642.6	642.8	642.9	643.3	644.2	645.0	645.9	646.7
130°	679.6	679.8	679.9	680.1	680.2	680.3	680.6	681.1	681.6	682.1	682.6
132.5°	713.9	714.2	714.6	714.9	715.2	715.4	715.7	716.4	717.1	717.8	718.5
135°	748.3	748.1	747.9	747.8	747.6	747.5	747.8	748.5	749.2	749.9	750.6
137.5°	778.8	778.8	778.8	778.8	778.8	778.8	779.2	780.1	780.9	781.8	782.6
140°	808.6	808.9	809.3	809.6	809.9	810.1	810.3	810.6	810.9	811.3	811.6
142.5°	835.3	836.0	836.7	837.4	838.1	838.4	838.5	838.6	838.8	838.9	839.1
145°	862.8	863.3	863.8	864.3	864.8	865.1	865.1	865.1	865.1	865.1	865.1
147.5°	884.2	885.2	886.2	887.3	888.3	888.8	888.7	888.5	888.4	888.2	888.0
150°	907.9	908.6	909.2	909.9	910.6	910.9	910.8	910.6	910.5	910.3	910.1
152.5°	927.7	928.2	928.7	929.2	929.7	930.0	929.8	929.5	929.2	928.8	928.5
155°	946.0	946.2	946.4	946.5	946.7	946.8	946.5	946.0	945.5	945.0	944.5
157.5°	962.1	962.1	962.1	962.1	962.1	962.1	961.8	961.1	960.4	959.7	959.0
160°	975.8	975.3	974.8	974.3	973.8	973.5	973.4	973.3	973.1	973.0	972.8
162.5°	988.0	987.3	986.7	986.0	985.3	985.0	984.9	984.7	984.6	984.4	984.2
165°	998.0	997.1	996.3	995.4	994.5	994.1	994.1	994.1	994.1	994.1	994.1
167.5°	1006.3	1005.5	1004.6	1003.8	1002.9	1002.5	1002.4	1002.3	1002.1	1002.0	1001.8
170°	1013.2	1012.2	1011.2	1010.1	1009.1	1008.6	1008.7	1008.9	1009.0	1009.2	1009.4
172.5°	1017.8	1016.8	1015.8	1014.7	1013.7	1013.2	1013.3	1013.5	1013.6	1013.8	1014.0
175°	1020.9	1019.9	1018.9	1017.8	1016.8	1016.3	1016.4	1016.5	1016.7	1016.8	1017.0
177.5°	1023.1	1021.9	1020.7	1019.6	1018.4	1017.8	1018.0	1018.3	1018.6	1019.0	1019.3
180°	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	599.3	604.3	604.8	609.4	608.0	605.7	609.9	607.1	612.6	610.8	613.1
5°	634.3	641.2	647.2	650.9	657.3	655.9	662.8	660.5	665.6	660.5	667.0
7.5°	675.3	686.8	692.8	702.4	705.2	705.7	714.0	715.8	719.0	715.8	719.5
10°	715.3	729.2	743.0	750.8	755.9	762.8	770.2	773.4	775.7	772.5	774.8
12.5°	751.7	773.4	788.6	804.2	807.9	813.9	821.7	820.8	830.0	828.2	832.3
15°	785.4	809.3	827.7	840.2	850.3	855.4	870.1	871.0	870.6	875.2	872.4
17.5°	815.3	835.6	861.8	877.9	890.4	890.4	898.7	915.7	914.3	913.9	916.6
20°	839.7	862.7	887.1	914.3	924.5	926.3	937.8	946.6	947.9	947.9	947.9
22.5°	858.1	885.3	911.6	930.9	938.7	945.2	955.3	960.8	962.7	961.8	962.7
25°	867.3	893.1	919.9	937.4	942.0	945.6	946.6	949.8	949.3	943.8	947.0
27.5°	869.2	894.1	911.6	916.2	913.9	911.6	896.8	898.2	894.1	885.8	889.0
30°	860.9	874.2	873.8	859.5	855.4	845.7	832.3	812.5	796.4	789.5	791.8
32.5°	831.0	831.0	814.4	782.1	767.8	750.3	726.4	708.4	687.2	682.6	691.4
35°	789.5	766.0	735.6	693.2	671.6	658.7	617.2	604.3	586.4	581.3	585.4
37.5°	725.0	685.9	641.6	602.0	583.6	560.6	524.2	505.8	492.9	484.1	488.3
40°	652.7	605.2	559.2	510.4	490.1	471.2	444.0	427.5	406.7	407.6	409.0
42.5°	583.6	527.9	476.3	431.1	411.8	396.1	377.2	357.0	349.6	347.3	345.0
45°	510.4	450.9	402.6	369.0	351.5	336.7	319.2	307.7	298.9	297.1	299.4
47.5°	441.3	391.1	345.0	313.7	299.4	292.0	278.2	267.6	262.1	257.5	260.2
50°	378.6	331.6	294.8	268.5	258.4	253.3	240.4	234.9	229.4	228.0	227.5
52.5°	327.0	287.0	255.2	234.0	226.2	223.4	213.7	205.9	201.3	202.7	203.6
55°	280.1	246.0	221.1	204.1	197.6	194.4	187.5	181.9	178.7	177.3	178.3
57.5°	238.6	209.1	191.2	177.3	172.3	170.9	163.5	161.7	159.4	158.0	158.0
60°	200.8	180.1	163.5	155.7	150.2	148.8	143.3	140.9	140.5	139.1	138.2
62.5°	169.0	152.0	140.5	132.2	129.9	129.4	125.7	123.0	121.6	120.7	120.7
65°	141.4	129.0	119.3	113.3	111.5	110.5	106.4	105.5	104.6	103.6	103.2
67.5°	117.9	106.9	100.0	95.8	93.5	94.0	91.7	89.8	89.8	89.4	88.9
70°	95.3	88.4	82.5	80.1	79.2	78.3	77.4	76.0	75.5	75.5	75.5
72.5°	75.1	70.5	67.2	65.9	64.9	64.0	63.1	63.1	63.1	62.6	62.6
75°	57.6	55.7	53.4	52.0	52.0	53.0	51.6	50.2	48.8	47.9	48.4
77.5°	43.3	42.4	41.0	38.7	39.2	38.2	38.2	37.3	37.8	37.8	36.8
80°	31.8	30.4	29.9	28.6	29.0	28.6	28.1	28.1	27.2	27.2	27.2
82.5°	22.1	20.7	20.7	20.3	19.8	19.8	19.3	19.3	19.8	18.9	18.9
85°	13.4	12.9	12.9	12.0	12.0	12.0	12.0	12.4	12.0	11.5	11.5
87.5°	6.0	6.4	6.0	5.5	5.5	5.5	5.1	5.1	4.6	5.1	5.1
90°	17.8	18.8	19.9	20.9	21.4	21.6	21.9	22.2	22.6	22.9	22.6
92.5°	17.0	18.0	19.1	20.1	20.6	20.6	20.6	20.6	20.6	20.6	20.6
95°	17.8	18.8	19.9	20.9	21.4	21.5	21.6	21.8	21.9	22.1	21.9
97.5°	17.6	18.5	19.3	20.2	20.6	20.7	20.9	21.0	21.2	21.4	21.2
100°	30.7	27.8	24.9	22.0	20.6	20.7	20.9	21.0	21.2	21.4	21.2
102.5°	155.7	117.5	79.4	41.2	22.1	22.1	22.1	22.1	22.1	22.1	22.1
105°	239.7	241.3	242.8	244.3	245.1	242.0	235.9	229.8	223.7	217.6	223.7
107.5°	287.9	288.8	289.6	290.5	290.9	291.2	291.9	292.6	293.3	294.0	293.3
110°	337.0	337.4	337.7	338.0	338.2	338.5	339.0	339.5	340.0	340.5	340.0

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	384.6	384.5	384.3	384.2	384.1	384.4	385.1	385.8	386.4	387.1	386.4
115°	431.0	431.3	431.7	432.0	432.2	432.2	432.2	432.2	432.2	432.2	432.2
117.5°	479.3	479.1	479.0	478.8	478.7	478.7	478.7	478.7	478.7	478.7	478.7
120°	522.6	523.0	523.3	523.6	523.8	523.6	523.3	523.0	522.6	522.3	522.6
122.5°	566.0	566.1	566.3	566.4	566.5	566.3	566.0	565.7	565.3	565.0	565.3
125°	605.2	605.7	606.2	606.7	607.0	607.1	607.3	607.4	607.6	607.8	607.6
127.5°	646.5	646.4	646.2	646.1	646.0	645.9	645.7	645.6	645.4	645.2	645.4
130°	682.8	683.0	683.1	683.3	683.4	683.4	683.4	683.4	683.4	683.4	683.4
132.5°	718.7	718.9	719.0	719.2	719.3	719.2	719.0	718.9	718.7	718.5	718.7
135°	750.9	751.3	751.6	751.9	752.1	752.3	752.6	752.9	753.3	753.6	753.3
137.5°	783.0	783.3	783.7	784.0	784.2	784.1	783.9	783.8	783.6	783.4	783.6
140°	812.1	812.6	813.1	813.6	813.9	814.0	814.2	814.3	814.5	814.7	814.5
142.5°	839.5	839.8	840.2	840.5	840.7	840.7	840.7	840.7	840.7	840.7	840.7
145°	865.3	865.5	865.6	865.8	865.9	866.1	866.4	866.7	867.1	867.4	867.1
147.5°	888.2	888.4	888.5	888.7	888.8	888.9	889.0	889.2	889.3	889.5	889.3
150°	910.1	910.1	910.1	910.1	910.1	910.2	910.4	910.5	910.7	910.9	910.7
152.5°	928.8	929.2	929.5	929.8	930.0	929.9	929.7	929.6	929.4	929.2	929.4
155°	945.2	945.9	946.6	947.3	947.6	947.3	946.8	946.3	945.8	945.3	945.8
157.5°	959.8	960.7	961.5	962.4	962.8	962.4	961.5	960.7	959.8	959.0	959.8
160°	973.8	974.8	975.8	976.8	977.3	976.8	975.8	974.8	973.8	972.8	973.8
162.5°	985.2	986.2	987.3	988.3	988.8	988.2	987.0	985.8	984.6	983.4	984.6
165°	995.5	996.8	998.2	999.5	1000.2	999.4	997.9	996.4	994.9	993.4	994.9
167.5°	1003.3	1004.8	1006.3	1007.8	1008.6	1007.8	1006.1	1004.4	1002.7	1001.0	1002.7
170°	1010.8	1012.1	1013.5	1014.8	1015.5	1014.7	1013.0	1011.3	1009.6	1007.9	1009.6
172.5°	1015.4	1016.7	1018.1	1019.4	1020.1	1019.2	1017.3	1015.4	1013.6	1011.7	1013.6
175°	1018.5	1020.1	1021.6	1023.1	1023.9	1022.9	1020.8	1018.8	1016.7	1014.7	1016.7
177.5°	1020.7	1022.0	1023.4	1024.7	1025.4	1024.4	1022.4	1020.3	1018.3	1016.3	1018.3
180°	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	614.5	611.2	610.8	610.8	605.7	608.5	602.9	597.0	594.2	594.2	589.1
5°	665.6	662.4	659.1	654.1	654.1	651.3	642.6	633.8	627.4	621.8	615.8
7.5°	718.1	714.9	705.7	700.6	703.4	697.8	686.3	671.6	660.5	651.8	639.3
10°	775.2	766.5	761.9	759.1	749.4	743.4	730.1	708.4	694.6	683.1	667.0
12.5°	821.7	824.5	807.0	808.4	798.7	790.4	769.7	749.0	728.2	712.1	688.2
15°	871.9	863.7	853.1	844.8	841.5	831.4	813.9	786.3	763.7	738.4	711.2
17.5°	911.6	905.1	895.0	887.1	880.2	855.8	841.1	816.7	785.8	760.9	727.8
20°	945.2	939.2	924.9	919.9	907.4	889.9	868.7	831.0	803.3	776.1	743.9
22.5°	959.5	953.5	941.0	934.6	926.8	909.7	889.4	853.5	819.4	785.4	751.3
25°	947.5	947.5	941.5	939.2	932.3	917.1	896.4	866.0	829.6	792.7	752.2
27.5°	889.4	901.0	905.1	907.4	907.4	907.9	893.6	864.1	828.6	792.7	750.3
30°	805.6	825.0	842.0	847.1	855.8	865.5	871.5	857.2	825.4	787.7	745.3
32.5°	700.1	725.0	756.8	764.6	776.6	805.6	821.7	827.7	810.2	777.1	731.9
35°	595.1	626.4	645.8	669.7	680.8	723.6	759.6	781.2	777.1	757.3	716.3
37.5°	503.5	521.4	544.9	570.2	592.4	633.3	678.0	719.9	737.0	727.3	696.5
40°	415.5	436.7	464.8	485.5	500.7	541.7	597.0	642.6	679.9	685.9	667.0
42.5°	353.3	374.5	391.5	414.1	426.1	465.7	514.5	571.6	615.8	639.3	631.0
45°	305.4	318.3	332.1	345.0	359.7	394.7	439.9	502.5	552.3	585.4	588.7
47.5°	263.5	275.0	287.0	298.9	307.2	334.4	375.9	427.0	481.3	526.9	544.9
50°	234.0	239.5	248.3	255.2	264.9	288.3	321.5	365.7	423.3	472.6	496.1
52.5°	205.0	211.9	218.8	224.8	231.2	247.8	278.2	316.4	366.2	416.9	445.9
55°	180.6	186.1	192.5	196.7	200.4	215.1	238.1	267.6	310.5	358.4	394.3
57.5°	160.8	163.1	168.6	170.9	175.0	187.0	203.6	229.8	264.4	310.9	340.4
60°	139.1	143.7	147.9	149.7	152.9	161.2	172.7	197.1	227.1	261.2	294.8
62.5°	121.6	123.4	126.7	129.0	131.3	140.0	149.7	168.1	190.7	219.3	250.1
65°	105.5	106.4	108.2	111.5	112.9	119.3	124.8	138.2	159.4	181.0	211.9
67.5°	88.9	89.8	92.1	94.0	95.3	99.5	105.5	115.2	126.7	150.6	167.7
70°	76.0	76.0	77.4	78.3	79.7	81.5	84.8	92.1	102.7	117.9	133.6
72.5°	63.6	63.6	63.6	64.9	64.9	66.3	68.2	73.2	80.6	92.6	102.7
75°	49.3	49.7	50.7	50.7	51.1	53.0	54.4	55.7	59.4	67.2	76.5
77.5°	37.3	38.2	38.7	37.8	38.7	38.7	40.5	42.4	44.2	46.5	53.4
80°	27.6	28.1	27.2	27.6	27.6	28.6	29.5	29.0	29.9	32.7	34.5
82.5°	18.4	18.9	18.9	18.9	18.9	20.3	20.3	19.8	20.3	20.7	21.2
85°	11.5	11.1	11.1	11.5	11.1	11.1	11.5	12.0	11.5	12.0	12.4
87.5°	5.1	5.1	5.1	5.1	4.6	4.6	5.1	4.6	5.1	4.6	4.1
90°	22.2	21.9	21.6	21.4	20.9	19.9	18.8	17.8	16.8	15.4	14.1
92.5°	20.6	20.6	20.6	20.6	20.1	19.1	18.0	17.0	16.0	14.6	13.3
95°	21.8	21.6	21.5	21.4	20.9	19.9	18.8	17.8	16.8	16.6	16.4
97.5°	21.0	20.9	20.7	20.6	20.2	19.3	18.5	17.6	16.8	34.6	52.4
100°	21.0	20.9	20.7	20.6	22.0	24.9	27.8	30.7	33.6	57.0	80.4
102.5°	22.1	22.1	22.1	22.1	41.2	79.4	117.5	155.7	193.9	191.9	189.9
105°	229.8	235.9	242.0	245.1	244.3	242.8	241.3	239.7	238.2	237.4	236.5
107.5°	292.6	291.9	291.2	290.9	290.5	289.6	288.8	287.9	287.1	285.9	284.7
110°	339.5	339.0	338.5	338.2	338.0	337.7	337.4	337.0	336.7	335.7	334.7

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	385.8	385.1	384.4	384.1	384.2	384.3	384.5	384.6	384.8	384.5	384.1
115°	432.2	432.2	432.2	432.2	432.0	431.7	431.3	431.0	430.6	430.8	431.0
117.5°	478.7	478.7	478.7	478.7	478.8	479.0	479.1	479.3	479.5	479.0	478.5
120°	523.0	523.3	523.6	523.8	523.6	523.3	523.0	522.6	522.3	522.5	522.6
122.5°	565.7	566.0	566.3	566.5	566.4	566.3	566.1	566.0	565.8	565.5	565.1
125°	607.4	607.3	607.1	607.0	606.7	606.2	605.7	605.2	604.7	605.1	605.4
127.5°	645.6	645.7	645.9	646.0	646.1	646.2	646.4	646.5	646.7	645.9	645.0
130°	683.4	683.4	683.4	683.4	683.3	683.1	683.0	682.8	682.6	682.1	681.6
132.5°	718.9	719.0	719.2	719.3	719.2	719.0	718.9	718.7	718.5	717.8	717.1
135°	752.9	752.6	752.3	752.1	751.9	751.6	751.3	750.9	750.6	749.9	749.2
137.5°	783.8	783.9	784.1	784.2	784.0	783.7	783.3	783.0	782.6	781.8	780.9
140°	814.3	814.2	814.0	813.9	813.6	813.1	812.6	812.1	811.6	811.3	810.9
142.5°	840.7	840.7	840.7	840.7	840.5	840.2	839.8	839.5	839.1	838.9	838.8
145°	866.7	866.4	866.1	865.9	865.8	865.6	865.5	865.3	865.1	865.1	865.1
147.5°	889.2	889.0	888.9	888.8	888.7	888.5	888.4	888.2	888.0	888.2	888.4
150°	910.5	910.4	910.2	910.1	910.1	910.1	910.1	910.1	910.1	910.3	910.5
152.5°	929.6	929.7	929.9	930.0	929.8	929.5	929.2	928.8	928.5	928.8	929.2
155°	946.3	946.8	947.3	947.6	947.3	946.6	945.9	945.2	944.5	945.0	945.5
157.5°	960.7	961.5	962.4	962.8	962.4	961.5	960.7	959.8	959.0	959.7	960.4
160°	974.8	975.8	976.8	977.3	976.8	975.8	974.8	973.8	972.8	973.0	973.1
162.5°	985.8	987.0	988.2	988.8	988.3	987.3	986.2	985.2	984.2	984.4	984.6
165°	996.4	997.9	999.4	1000.2	999.5	998.2	996.8	995.5	994.1	994.1	994.1
167.5°	1004.4	1006.1	1007.8	1008.6	1007.8	1006.3	1004.8	1003.3	1001.8	1002.0	1002.1
170°	1011.3	1013.0	1014.7	1015.5	1014.8	1013.5	1012.1	1010.8	1009.4	1009.2	1009.0
172.5°	1015.4	1017.3	1019.2	1020.1	1019.4	1018.1	1016.7	1015.4	1014.0	1013.8	1013.6
175°	1018.8	1020.8	1022.9	1023.9	1023.1	1021.6	1020.1	1018.5	1017.0	1016.8	1016.7
177.5°	1020.3	1022.4	1024.4	1025.4	1024.7	1023.4	1022.0	1020.7	1019.3	1019.0	1018.6
180°	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	586.4	584.1	582.7	582.2	578.1	575.8	574.4	573.5	572.1	568.4	565.2
5°	608.5	602.0	598.8	595.1	588.7	581.3	575.3	571.6	567.0	559.6	552.7
7.5°	629.2	619.5	613.1	608.0	597.0	585.0	575.3	567.5	558.7	548.6	538.9
10°	650.9	635.2	626.9	619.1	602.9	587.3	573.5	562.0	549.5	536.2	525.6
12.5°	667.9	647.2	638.0	626.9	607.1	588.7	571.2	555.5	539.4	525.1	509.9
15°	687.7	661.9	651.3	637.0	609.9	585.9	563.3	546.3	529.7	508.5	492.4
17.5°	699.2	669.3	654.1	641.6	612.2	583.1	556.9	535.7	516.4	495.2	478.1
20°	710.7	676.6	659.6	642.1	607.1	576.2	548.6	523.3	503.0	480.0	462.5
22.5°	714.4	674.8	656.8	640.7	603.9	569.3	537.5	511.7	488.3	465.2	445.4
25°	714.4	674.3	653.2	632.4	593.7	558.3	526.5	498.4	472.1	449.1	429.3
27.5°	707.0	665.1	643.0	624.1	584.1	545.8	513.1	482.3	456.9	433.9	411.3
30°	697.8	651.8	629.7	607.1	568.4	532.0	496.5	468.0	441.3	415.0	394.7
32.5°	686.3	637.5	613.1	590.0	549.1	511.3	478.6	450.5	425.1	398.0	375.4
35°	669.7	616.3	589.1	568.9	529.2	490.1	458.8	431.1	406.7	378.6	354.2
37.5°	648.5	597.0	569.3	544.4	503.5	467.5	438.0	411.3	387.4	361.6	334.4
40°	623.7	569.8	545.8	519.6	476.3	442.2	414.6	390.6	366.7	342.2	316.0
42.5°	595.6	542.1	515.4	490.1	448.6	415.0	389.2	367.6	345.5	322.9	294.8
45°	562.0	511.7	486.0	462.0	421.9	387.4	363.9	343.2	324.3	301.2	276.4
47.5°	524.2	480.4	454.2	428.4	389.2	359.3	336.2	318.7	302.6	279.6	257.0
50°	487.3	444.0	422.8	396.6	360.7	332.6	309.1	294.3	281.9	259.3	239.1
52.5°	440.8	408.1	387.8	365.3	330.7	302.2	283.7	270.8	256.1	238.6	220.6
55°	399.8	369.4	353.3	332.1	298.0	272.7	257.0	245.0	233.5	217.9	203.6
57.5°	353.3	334.4	318.3	299.9	266.2	244.6	230.8	220.6	210.0	197.1	185.6
60°	304.5	295.7	280.1	265.3	236.8	217.9	206.4	197.1	187.0	176.4	166.7
62.5°	261.2	256.1	246.9	235.4	208.7	192.5	181.0	174.1	166.7	157.1	147.9
65°	220.2	217.9	209.1	200.8	182.4	168.1	158.0	153.8	145.6	138.2	129.9
67.5°	183.8	181.0	176.0	172.3	156.6	143.3	138.2	132.7	125.7	120.2	113.3
70°	146.9	146.5	143.3	138.6	130.4	120.7	115.6	111.9	105.0	100.9	95.8
72.5°	114.2	116.5	113.8	111.9	106.4	99.5	94.9	92.6	87.1	83.8	80.1
75°	85.2	87.1	88.4	85.2	83.8	80.6	76.5	74.2	71.4	66.8	65.4
77.5°	58.0	62.2	62.2	63.1	63.6	61.7	58.5	56.7	53.4	52.5	50.7
80°	38.2	41.9	42.4	43.3	44.7	44.7	42.4	41.9	38.7	38.2	36.8
82.5°	22.1	25.3	27.2	28.6	28.1	29.9	28.1	27.6	25.8	25.8	24.9
85°	12.0	12.4	13.4	14.3	15.2	16.1	16.1	15.7	15.2	14.7	13.8
87.5°	4.6	4.6	5.1	4.6	5.1	6.0	6.4	6.4	6.0	5.5	4.6
90°	12.7	11.4	10.7	9.8	7.9	6.0	4.2	2.3	4.2	6.0	7.9
92.5°	11.9	10.6	9.9	10.1	10.4	10.8	11.1	11.5	11.1	10.8	10.4
95°	16.3	16.1	16.0	18.9	24.7	30.4	36.2	42.0	36.2	30.4	24.7
97.5°	70.3	88.1	97.0	95.1	91.4	87.7	83.9	80.2	83.9	87.7	91.4
100°	103.9	127.3	139.0	137.5	134.4	131.3	128.3	125.2	128.3	131.3	134.4
102.5°	187.8	185.8	184.8	183.8	181.7	179.7	177.6	175.6	177.6	179.7	181.7
105°	235.7	234.8	234.4	233.9	232.9	231.8	230.8	229.8	230.8	231.8	232.9
107.5°	283.5	282.3	281.7	281.5	281.0	280.5	280.0	279.5	280.0	280.5	281.0
110°	333.6	332.6	332.1	331.9	331.4	330.9	330.4	329.9	330.4	330.9	331.4

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	383.8	383.5	383.3	382.8	381.8	380.7	379.7	378.7	379.7	380.7	381.8
115°	431.1	431.3	431.4	431.1	430.6	430.1	429.6	429.1	429.6	430.1	430.6
117.5°	478.0	477.5	477.2	476.9	476.2	475.5	474.9	474.2	474.9	475.5	476.2
120°	522.8	522.9	523.0	522.7	522.0	521.3	520.7	520.0	520.7	521.3	522.0
122.5°	564.8	564.5	564.3	564.1	563.8	563.4	563.1	562.7	563.1	563.4	563.8
125°	605.8	606.1	606.3	606.0	605.3	604.6	603.9	603.2	603.9	604.6	605.3
127.5°	644.2	643.3	642.9	642.8	642.6	642.5	642.3	642.1	642.3	642.5	642.6
130°	681.1	680.6	680.3	680.2	680.1	679.9	679.8	679.6	679.8	679.9	680.1
132.5°	716.4	715.7	715.4	715.2	714.9	714.6	714.2	713.9	714.2	714.6	714.9
135°	748.5	747.8	747.5	747.6	747.8	747.9	748.1	748.3	748.1	747.9	747.8
137.5°	780.1	779.2	778.8	778.8	778.8	778.8	778.8	778.8	778.8	778.8	778.8
140°	810.6	810.3	810.1	809.9	809.6	809.3	808.9	808.6	808.9	809.3	809.6
142.5°	838.6	838.5	838.4	838.1	837.4	836.7	836.0	835.3	836.0	836.7	837.4
145°	865.1	865.1	865.1	864.8	864.3	863.8	863.3	862.8	863.3	863.8	864.3
147.5°	888.5	888.7	888.8	888.3	887.3	886.2	885.2	884.2	885.2	886.2	887.3
150°	910.6	910.8	910.9	910.6	909.9	909.2	908.6	907.9	908.6	909.2	909.9
152.5°	929.5	929.8	930.0	929.7	929.2	928.7	928.2	927.7	928.2	928.7	929.2
155°	946.0	946.5	946.8	946.7	946.5	946.4	946.2	946.0	946.2	946.4	946.5
157.5°	961.1	961.8	962.1	962.1	962.1	962.1	962.1	962.1	962.1	962.1	962.1
160°	973.3	973.4	973.5	973.8	974.3	974.8	975.3	975.8	975.3	974.8	974.3
162.5°	984.7	984.9	985.0	985.3	986.0	986.7	987.3	988.0	987.3	986.7	986.0
165°	994.1	994.1	994.1	994.5	995.4	996.3	997.1	998.0	997.1	996.3	995.4
167.5°	1002.3	1002.4	1002.5	1002.9	1003.8	1004.6	1005.5	1006.3	1005.5	1004.6	1003.8
170°	1008.9	1008.7	1008.6	1009.1	1010.1	1011.2	1012.2	1013.2	1012.2	1011.2	1010.1
172.5°	1013.5	1013.3	1013.2	1013.7	1014.7	1015.8	1016.8	1017.8	1016.8	1015.8	1014.7
175°	1016.5	1016.4	1016.3	1016.8	1017.8	1018.9	1019.9	1020.9	1019.9	1018.9	1017.8
177.5°	1018.3	1018.0	1017.8	1018.4	1019.6	1020.7	1021.9	1023.1	1021.9	1020.7	1019.6
180°	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	562.4	561.5	560.6	556.9	553.7	548.1	543.5	541.7	541.2	541.7	540.3
5°	546.3	545.8	542.6	536.2	530.2	523.7	519.1	514.5	511.7	511.7	508.5
7.5°	531.1	527.9	525.1	516.8	509.9	501.2	494.2	490.1	487.8	482.7	482.7
10°	515.0	510.4	506.7	498.8	488.7	480.0	471.2	466.1	462.0	458.3	456.9
12.5°	498.8	495.2	488.3	480.0	469.8	458.8	449.6	445.9	436.2	428.4	428.8
15°	483.6	475.4	472.1	460.2	448.2	437.6	424.2	413.6	405.8	400.7	394.3
17.5°	466.6	458.3	452.3	442.2	426.5	409.9	397.1	382.8	374.9	366.2	362.0
20°	447.7	440.8	436.2	420.1	401.2	381.4	367.1	358.4	349.6	343.2	339.5
22.5°	431.6	422.8	417.3	395.7	374.9	355.1	344.1	336.7	329.3	323.8	322.0
25°	410.9	405.8	392.4	373.6	348.2	334.9	325.2	315.5	311.4	307.7	303.5
27.5°	393.8	381.4	372.2	347.3	331.6	316.4	306.8	299.4	294.3	290.6	287.4
30°	372.6	361.1	348.2	327.5	313.2	298.9	290.2	284.2	278.7	276.4	273.6
32.5°	350.5	339.9	327.5	310.9	293.4	282.4	275.4	269.0	265.3	263.0	259.8
35°	330.7	317.4	309.1	293.4	279.1	266.7	260.2	254.7	250.6	249.7	249.2
37.5°	309.5	299.4	291.6	275.4	263.5	252.9	246.9	240.9	238.6	238.1	236.3
40°	291.1	282.4	275.0	259.8	246.9	237.2	232.6	228.9	226.6	226.6	226.2
42.5°	275.0	265.8	258.4	244.6	233.1	224.3	219.3	215.6	214.6	215.1	214.6
45°	257.0	249.2	241.8	227.5	217.9	211.4	205.9	204.1	202.7	203.1	203.6
47.5°	240.0	233.5	226.2	214.6	203.6	196.7	193.5	191.6	191.6	191.6	192.5
50°	224.8	217.4	211.0	199.0	188.9	183.3	180.6	178.3	178.7	179.2	179.6
52.5°	206.8	200.4	195.8	183.8	176.4	169.5	166.3	166.7	166.3	166.3	167.2
55°	191.2	184.7	180.1	169.0	161.7	157.1	154.3	152.9	153.4	152.5	154.3
57.5°	173.7	168.1	164.9	154.3	147.9	143.7	141.4	139.1	140.0	139.6	139.1
60°	158.5	152.0	146.9	139.6	134.0	129.0	127.6	125.3	126.2	125.3	124.8
62.5°	140.9	135.9	132.2	124.8	120.2	116.1	112.9	111.5	111.0	109.6	108.2
65°	123.4	120.7	117.0	109.6	105.0	101.8	100.0	98.6	98.1	94.4	90.3
67.5°	107.3	105.5	101.8	96.3	92.1	88.9	86.1	83.8	81.1	78.3	76.0
70°	92.1	89.4	87.1	82.0	78.3	75.1	72.3	69.6	68.2	65.4	64.5
72.5°	77.4	74.6	72.3	67.7	64.5	61.3	60.3	57.1	55.7	55.3	55.3
75°	62.2	59.9	58.5	54.4	51.6	49.3	47.9	47.0	46.1	45.1	43.8
77.5°	47.4	46.1	45.1	42.4	40.1	38.7	38.2	35.0	34.1	33.2	32.2
80°	34.5	34.1	33.2	30.9	29.9	26.7	26.7	25.8	25.3	25.3	25.3
82.5°	23.5	22.6	22.1	19.8	19.3	18.9	18.4	18.0	18.4	18.0	18.4
85°	12.4	12.0	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.1	11.5
87.5°	4.6	4.6	4.6	4.6	4.1	4.6	4.6	4.1	4.6	4.6	4.6
90°	9.8	10.7	11.4	12.7	14.1	15.4	16.8	17.8	18.8	19.9	20.9
92.5°	10.1	9.9	10.6	11.9	13.3	14.6	16.0	17.0	18.0	19.1	20.1
95°	18.9	16.0	16.1	16.3	16.4	16.6	16.8	17.8	18.8	19.9	20.9
97.5°	95.1	97.0	88.1	70.3	52.4	34.6	16.8	17.6	18.5	19.3	20.2
100°	137.5	139.0	127.3	103.9	80.4	57.0	33.6	30.7	27.8	24.9	22.0
102.5°	183.8	184.8	185.8	187.8	189.9	191.9	193.9	155.7	117.5	79.4	41.2
105°	233.9	234.4	234.8	235.7	236.5	237.4	238.2	239.7	241.3	242.8	244.3
107.5°	281.5	281.7	282.3	283.5	284.7	285.9	287.1	287.9	288.8	289.6	290.5
110°	331.9	332.1	332.6	333.6	334.7	335.7	336.7	337.0	337.4	337.7	338.0

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	382.8	383.3	383.5	383.8	384.1	384.5	384.8	384.6	384.5	384.3	384.2
115°	431.1	431.4	431.3	431.1	431.0	430.8	430.6	431.0	431.3	431.7	432.0
117.5°	476.9	477.2	477.5	478.0	478.5	479.0	479.5	479.3	479.1	479.0	478.8
120°	522.7	523.0	522.9	522.8	522.6	522.5	522.3	522.6	523.0	523.3	523.6
122.5°	564.1	564.3	564.5	564.8	565.1	565.5	565.8	566.0	566.1	566.3	566.4
125°	606.0	606.3	606.1	605.8	605.4	605.1	604.7	605.2	605.7	606.2	606.7
127.5°	642.8	642.9	643.3	644.2	645.0	645.9	646.7	646.5	646.4	646.2	646.1
130°	680.2	680.3	680.6	681.1	681.6	682.1	682.6	682.8	683.0	683.1	683.3
132.5°	715.2	715.4	715.7	716.4	717.1	717.8	718.5	718.7	718.9	719.0	719.2
135°	747.6	747.5	747.8	748.5	749.2	749.9	750.6	750.9	751.3	751.6	751.9
137.5°	778.8	778.8	779.2	780.1	780.9	781.8	782.6	783.0	783.3	783.7	784.0
140°	809.9	810.1	810.3	810.6	810.9	811.3	811.6	812.1	812.6	813.1	813.6
142.5°	838.1	838.4	838.5	838.6	838.8	838.9	839.1	839.5	839.8	840.2	840.5
145°	864.8	865.1	865.1	865.1	865.1	865.1	865.1	865.3	865.5	865.6	865.8
147.5°	888.3	888.8	888.7	888.5	888.4	888.2	888.0	888.2	888.4	888.5	888.7
150°	910.6	910.9	910.8	910.6	910.5	910.3	910.1	910.1	910.1	910.1	910.1
152.5°	929.7	930.0	929.8	929.5	929.2	928.8	928.5	928.8	929.2	929.5	929.8
155°	946.7	946.8	946.5	946.0	945.5	945.0	944.5	945.2	945.9	946.6	947.3
157.5°	962.1	962.1	961.8	961.1	960.4	959.7	959.0	959.8	960.7	961.5	962.4
160°	973.8	973.5	973.4	973.3	973.1	973.0	972.8	973.8	974.8	975.8	976.8
162.5°	985.3	985.0	984.9	984.7	984.6	984.4	984.2	985.2	986.2	987.3	988.3
165°	994.5	994.1	994.1	994.1	994.1	994.1	994.1	995.5	996.8	998.2	999.5
167.5°	1002.9	1002.5	1002.4	1002.3	1002.1	1002.0	1001.8	1003.3	1004.8	1006.3	1007.8
170°	1009.1	1008.6	1008.7	1008.9	1009.0	1009.2	1009.4	1010.8	1012.1	1013.5	1014.8
172.5°	1013.7	1013.2	1013.3	1013.5	1013.6	1013.8	1014.0	1015.4	1016.7	1018.1	1019.4
175°	1016.8	1016.3	1016.4	1016.5	1016.7	1016.8	1017.0	1018.5	1020.1	1021.6	1023.1
177.5°	1018.4	1017.8	1018.0	1018.3	1018.6	1019.0	1019.3	1020.7	1022.0	1023.4	1024.7
180°	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	540.3	542.1	539.8	541.2	538.0	537.5	538.0	538.0	538.5	538.9	539.4
5°	509.9	509.4	506.7	504.8	503.5	504.8	505.8	506.7	505.8	506.7	507.1
7.5°	481.3	480.0	478.6	475.4	476.3	475.4	478.1	476.7	476.7	479.0	480.9
10°	456.0	453.2	452.3	448.6	445.9	445.4	448.6	450.0	451.4	452.3	456.0
12.5°	423.3	419.2	415.9	417.3	409.5	412.7	413.6	411.8	417.3	423.8	420.1
15°	388.3	388.8	382.3	380.0	373.6	375.4	375.9	380.5	385.1	384.6	390.1
17.5°	362.5	359.7	354.2	353.8	351.0	352.4	351.9	355.6	354.2	356.5	361.1
20°	338.6	336.7	332.1	330.3	331.2	330.3	330.7	331.2	332.6	337.6	336.7
22.5°	319.7	317.4	317.4	315.1	312.3	311.4	313.7	315.1	316.9	317.8	320.1
25°	303.1	301.2	298.9	297.6	295.3	295.7	297.1	298.9	300.3	302.2	304.0
27.5°	286.0	286.0	283.7	283.3	282.4	281.9	283.7	284.7	284.7	286.0	287.9
30°	272.7	272.7	270.4	269.9	269.5	269.5	270.8	271.3	271.8	273.1	274.1
32.5°	259.8	259.3	258.4	258.9	258.4	258.9	258.9	259.3	260.2	260.7	262.6
35°	247.8	248.3	247.4	247.4	246.9	247.4	248.3	248.7	249.2	250.1	250.1
37.5°	236.3	237.2	236.8	238.1	238.1	238.1	238.1	239.1	239.1	239.1	238.6
40°	226.2	226.2	225.7	226.6	227.5	227.5	228.0	228.0	228.5	228.5	228.0
42.5°	214.6	215.6	217.0	217.4	218.3	217.9	219.3	218.8	219.3	218.3	217.4
45°	204.1	204.1	205.9	207.7	208.2	208.2	208.2	209.1	208.2	206.8	206.4
47.5°	192.5	193.5	194.4	196.7	197.1	197.1	197.1	197.1	196.2	196.2	196.2
50°	181.0	181.5	181.9	182.9	184.2	183.8	183.8	183.8	185.6	183.8	184.2
52.5°	167.2	167.7	168.1	170.0	169.5	169.5	170.0	170.0	171.3	170.9	170.0
55°	153.4	153.4	154.3	154.3	154.3	155.2	155.7	156.6	156.1	156.6	157.1
57.5°	139.6	138.6	138.2	138.2	139.6	139.1	139.6	139.6	141.4	142.3	142.8
60°	123.4	123.4	123.0	120.2	120.2	119.8	121.1	122.1	123.0	127.1	126.7
62.5°	106.9	105.0	103.2	103.6	100.9	102.3	101.3	102.3	105.0	108.2	108.7
65°	90.3	88.9	87.1	86.6	85.7	87.1	86.6	87.1	88.4	90.3	92.6
67.5°	75.5	75.1	74.2	73.7	73.7	73.7	74.6	74.6	75.1	76.5	77.8
70°	64.5	64.0	64.5	63.6	64.0	63.6	64.0	64.5	64.9	65.4	66.8
72.5°	54.4	54.4	54.4	53.4	54.4	53.9	53.9	54.4	54.8	55.3	56.2
75°	43.3	42.4	41.5	40.5	40.1	41.0	41.5	41.0	42.4	44.2	44.2
77.5°	32.7	32.2	32.2	32.2	32.7	32.2	33.2	32.7	33.2	33.2	34.1
80°	25.3	24.9	25.3	25.3	24.9	25.8	25.3	25.3	25.8	26.3	25.8
82.5°	18.4	18.9	18.4	18.4	18.4	19.3	18.4	18.4	18.4	18.9	18.9
85°	11.5	11.5	11.5	11.5	12.0	11.5	12.0	11.5	12.4	12.0	12.0
87.5°	4.1	4.6	5.1	5.1	5.1	5.1	4.6	5.1	5.5	5.1	5.5
90°	21.4	21.6	21.9	22.2	22.6	22.9	22.6	22.2	21.9	21.6	21.4
92.5°	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6
95°	21.4	21.5	21.6	21.8	21.9	22.1	21.9	21.8	21.6	21.5	21.4
97.5°	20.6	20.7	20.9	21.0	21.2	21.4	21.2	21.0	20.9	20.7	20.6
100°	20.6	20.7	20.9	21.0	21.2	21.4	21.2	21.0	20.9	20.7	20.6
102.5°	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1
105°	245.1	242.0	235.9	229.8	223.7	217.6	223.7	229.8	235.9	242.0	245.1
107.5°	290.9	291.2	291.9	292.6	293.3	294.0	293.3	292.6	291.9	291.2	290.9
110°	338.2	338.5	339.0	339.5	340.0	340.5	340.0	339.5	339.0	338.5	338.2



TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	384.1	384.4	385.1	385.8	386.4	387.1	386.4	385.8	385.1	384.4	384.1
115°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
117.5°	478.7	478.7	478.7	478.7	478.7	478.7	478.7	478.7	478.7	478.7	478.7
120°	523.8	523.6	523.3	523.0	522.6	522.3	522.6	523.0	523.3	523.6	523.8
122.5°	566.5	566.3	566.0	565.7	565.3	565.0	565.3	565.7	566.0	566.3	566.5
125°	607.0	607.1	607.3	607.4	607.6	607.8	607.6	607.4	607.3	607.1	607.0
127.5°	646.0	645.9	645.7	645.6	645.4	645.2	645.4	645.6	645.7	645.9	646.0
130°	683.4	683.4	683.4	683.4	683.4	683.4	683.4	683.4	683.4	683.4	683.4
132.5°	719.3	719.2	719.0	718.9	718.7	718.5	718.7	718.9	719.0	719.2	719.3
135°	752.1	752.3	752.6	752.9	753.3	753.6	753.3	752.9	752.6	752.3	752.1
137.5°	784.2	784.1	783.9	783.8	783.6	783.4	783.6	783.8	783.9	784.1	784.2
140°	813.9	814.0	814.2	814.3	814.5	814.7	814.5	814.3	814.2	814.0	813.9
142.5°	840.7	840.7	840.7	840.7	840.7	840.7	840.7	840.7	840.7	840.7	840.7
145°	865.9	866.1	866.4	866.7	867.1	867.4	867.1	866.7	866.4	866.1	865.9
147.5°	888.8	888.9	889.0	889.2	889.3	889.5	889.3	889.2	889.0	888.9	888.8
150°	910.1	910.2	910.4	910.5	910.7	910.9	910.7	910.5	910.4	910.2	910.1
152.5°	930.0	929.9	929.7	929.6	929.4	929.2	929.4	929.6	929.7	929.9	930.0
155°	947.6	947.3	946.8	946.3	945.8	945.3	945.8	946.3	946.8	947.3	947.6
157.5°	962.8	962.4	961.5	960.7	959.8	959.0	959.8	960.7	961.5	962.4	962.8
160°	977.3	976.8	975.8	974.8	973.8	972.8	973.8	974.8	975.8	976.8	977.3
162.5°	988.8	988.2	987.0	985.8	984.6	983.4	984.6	985.8	987.0	988.2	988.8
165°	1000.2	999.4	997.9	996.4	994.9	993.4	994.9	996.4	997.9	999.4	1000.2
167.5°	1008.6	1007.8	1006.1	1004.4	1002.7	1001.0	1002.7	1004.4	1006.1	1007.8	1008.6
170°	1015.5	1014.7	1013.0	1011.3	1009.6	1007.9	1009.6	1011.3	1013.0	1014.7	1015.5
172.5°	1020.1	1019.2	1017.3	1015.4	1013.6	1011.7	1013.6	1015.4	1017.3	1019.2	1020.1
175°	1023.9	1022.9	1020.8	1018.8	1016.7	1014.7	1016.7	1018.8	1020.8	1022.9	1023.9
177.5°	1025.4	1024.4	1022.4	1020.3	1018.3	1016.3	1018.3	1020.3	1022.4	1024.4	1025.4
180°	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	541.2	543.5	542.6	539.4	540.8	543.5	546.3	550.0	552.3	554.1	555.0
5°	509.4	513.6	512.7	512.7	514.5	519.1	523.7	531.6	534.3	537.5	542.1
7.5°	481.3	484.6	487.3	488.3	491.0	497.0	503.0	511.7	518.7	522.3	525.1
10°	456.5	458.8	462.9	465.2	468.0	475.4	484.1	493.3	500.2	506.7	510.4
12.5°	424.7	433.9	439.4	443.1	446.8	457.9	464.8	474.9	483.2	489.2	494.7
15°	389.2	400.3	403.5	417.8	427.0	435.7	446.3	458.3	466.1	473.1	480.4
17.5°	359.3	367.1	370.8	386.0	393.8	407.6	422.8	438.0	450.0	455.1	462.5
20°	340.4	344.5	351.9	357.0	365.3	381.4	398.0	416.4	434.4	439.4	446.8
22.5°	321.0	326.6	331.6	338.6	345.0	356.1	372.6	392.9	412.3	421.5	430.2
25°	303.5	309.1	312.3	319.7	325.7	336.7	348.2	369.0	392.0	399.8	413.6
27.5°	289.7	293.0	298.5	301.7	308.6	318.7	329.3	345.0	367.6	380.9	394.3
30°	275.9	278.2	282.8	287.4	292.5	299.4	311.4	326.6	347.3	358.8	372.2
32.5°	262.1	265.8	268.5	271.8	277.3	285.6	293.9	308.6	325.2	338.1	351.5
35°	250.6	252.0	255.6	259.3	263.0	270.4	279.1	293.4	308.2	318.3	330.3
37.5°	238.1	240.4	243.2	244.6	250.6	255.2	264.4	275.4	293.0	299.4	311.4
40°	228.5	228.0	230.8	233.1	235.8	243.2	248.7	260.7	274.5	284.7	292.0
42.5°	216.5	216.5	217.4	220.2	223.9	228.5	234.9	245.0	259.3	266.7	275.4
45°	206.8	205.4	205.9	207.7	210.0	214.6	221.1	229.8	244.1	250.1	259.3
47.5°	195.3	193.9	193.9	195.8	197.6	200.8	205.9	216.0	227.5	235.4	242.3
50°	182.4	182.9	182.4	183.8	184.7	187.9	193.5	201.7	212.3	218.8	226.6
52.5°	170.4	169.5	169.0	170.0	171.8	174.1	180.1	187.5	197.6	204.1	211.0
55°	155.7	156.6	156.6	156.6	159.4	160.3	164.9	172.3	182.4	187.5	193.9
57.5°	142.3	141.9	142.8	142.3	144.6	147.9	151.5	157.1	167.2	172.3	178.3
60°	127.6	128.1	128.5	128.5	130.4	133.6	137.7	142.8	151.1	156.1	161.7
62.5°	109.6	111.9	114.2	115.2	117.9	120.2	123.0	128.5	135.9	139.6	144.6
65°	92.6	95.8	99.0	101.3	103.2	105.5	109.2	114.2	120.2	123.9	129.0
67.5°	77.8	80.1	84.3	86.6	90.3	93.0	95.3	99.5	106.9	108.2	112.4
70°	67.2	68.2	70.0	71.9	76.0	78.3	81.1	85.2	90.7	94.0	96.3
72.5°	56.7	57.1	58.0	59.9	61.7	64.5	67.7	71.4	76.5	77.8	81.1
75°	45.1	47.9	47.9	49.3	50.7	52.0	54.8	58.5	61.7	64.0	65.9
77.5°	33.6	35.0	35.9	38.2	40.1	41.5	43.3	46.1	47.9	49.7	51.1
80°	26.3	26.7	27.2	27.2	28.1	29.9	31.8	33.6	35.9	36.8	38.2
82.5°	19.3	19.3	19.3	20.3	20.7	21.2	21.2	22.1	24.4	25.3	26.7
85°	12.4	12.4	12.4	12.4	12.9	13.4	13.8	14.3	14.3	14.3	15.2
87.5°	5.1	6.0	5.5	6.0	6.0	6.0	6.0	6.4	6.4	6.9	6.9
90°	20.9	19.9	18.8	17.8	16.8	15.4	14.1	12.7	11.4	10.7	9.8
92.5°	20.1	19.1	18.0	17.0	16.0	14.6	13.3	11.9	10.6	9.9	10.1
95°	20.9	19.9	18.8	17.8	16.8	16.6	16.4	16.3	16.1	16.0	18.9
97.5°	20.2	19.3	18.5	17.6	16.8	34.6	52.4	70.3	88.1	97.0	95.1
100°	22.0	24.9	27.8	30.7	33.6	57.0	80.4	103.9	127.3	139.0	137.5
102.5°	41.2	79.4	117.5	155.7	193.9	191.9	189.9	187.8	185.8	184.8	183.8
105°	244.3	242.8	241.3	239.7	238.2	237.4	236.5	235.7	234.8	234.4	233.9
107.5°	290.5	289.6	288.8	287.9	287.1	285.9	284.7	283.5	282.3	281.7	281.5
110°	338.0	337.7	337.4	337.0	336.7	335.7	334.7	333.6	332.6	332.1	331.9

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	384.2	384.3	384.5	384.6	384.8	384.5	384.1	383.8	383.5	383.3	382.8
115°	432.0	431.7	431.3	431.0	430.6	430.8	431.0	431.1	431.3	431.4	431.1
117.5°	478.8	479.0	479.1	479.3	479.5	479.0	478.5	478.0	477.5	477.2	476.9
120°	523.6	523.3	523.0	522.6	522.3	522.5	522.6	522.8	522.9	523.0	522.7
122.5°	566.4	566.3	566.1	566.0	565.8	565.5	565.1	564.8	564.5	564.3	564.1
125°	606.7	606.2	605.7	605.2	604.7	605.1	605.4	605.8	606.1	606.3	606.0
127.5°	646.1	646.2	646.4	646.5	646.7	645.9	645.0	644.2	643.3	642.9	642.8
130°	683.3	683.1	683.0	682.8	682.6	682.1	681.6	681.1	680.6	680.3	680.2
132.5°	719.2	719.0	718.9	718.7	718.5	717.8	717.1	716.4	715.7	715.4	715.2
135°	751.9	751.6	751.3	750.9	750.6	749.9	749.2	748.5	747.8	747.5	747.6
137.5°	784.0	783.7	783.3	783.0	782.6	781.8	780.9	780.1	779.2	778.8	778.8
140°	813.6	813.1	812.6	812.1	811.6	811.3	810.9	810.6	810.3	810.1	809.9
142.5°	840.5	840.2	839.8	839.5	839.1	838.9	838.8	838.6	838.5	838.4	838.1
145°	865.8	865.6	865.5	865.3	865.1	865.1	865.1	865.1	865.1	865.1	864.8
147.5°	888.7	888.5	888.4	888.2	888.0	888.2	888.4	888.5	888.7	888.8	888.3
150°	910.1	910.1	910.1	910.1	910.1	910.3	910.5	910.6	910.8	910.9	910.6
152.5°	929.8	929.5	929.2	928.8	928.5	928.8	929.2	929.5	929.8	930.0	929.7
155°	947.3	946.6	945.9	945.2	944.5	945.0	945.5	946.0	946.5	946.8	946.7
157.5°	962.4	961.5	960.7	959.8	959.0	959.7	960.4	961.1	961.8	962.1	962.1
160°	976.8	975.8	974.8	973.8	972.8	973.0	973.1	973.3	973.4	973.5	973.8
162.5°	988.3	987.3	986.2	985.2	984.2	984.4	984.6	984.7	984.9	985.0	985.3
165°	999.5	998.2	996.8	995.5	994.1	994.1	994.1	994.1	994.1	994.1	994.5
167.5°	1007.8	1006.3	1004.8	1003.3	1001.8	1002.0	1002.1	1002.3	1002.4	1002.5	1002.9
170°	1014.8	1013.5	1012.1	1010.8	1009.4	1009.2	1009.0	1008.9	1008.7	1008.6	1009.1
172.5°	1019.4	1018.1	1016.7	1015.4	1014.0	1013.8	1013.6	1013.5	1013.3	1013.2	1013.7
175°	1023.1	1021.6	1020.1	1018.5	1017.0	1016.8	1016.7	1016.5	1016.4	1016.3	1016.8
177.5°	1024.7	1023.4	1022.0	1020.7	1019.3	1019.0	1018.6	1018.3	1018.0	1017.8	1018.4
180°	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9	1020.9

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	571.6	571.6	571.6	571.6
2.5°	558.7	561.5	566.1	572.5
5°	545.8	553.7	561.0	570.7
7.5°	534.3	543.5	553.7	567.5
10°	521.0	532.5	545.4	562.4
12.5°	505.3	521.4	536.2	554.6
15°	493.8	505.8	524.6	546.3
17.5°	477.7	493.8	512.7	537.1
20°	462.5	479.5	500.7	526.0
22.5°	446.3	465.7	486.9	514.0
25°	429.8	450.5	471.7	500.7
27.5°	414.6	433.4	457.4	486.9
30°	396.1	417.8	440.8	471.7
32.5°	378.2	400.7	424.2	455.1
35°	358.8	381.4	407.2	436.7
37.5°	339.9	364.8	388.3	416.9
40°	319.2	345.0	369.4	398.4
42.5°	298.9	325.7	350.1	374.9
45°	280.1	306.3	328.4	351.9
47.5°	262.1	285.6	308.2	329.3
50°	244.6	264.4	285.1	302.6
52.5°	226.2	245.0	261.6	277.3
55°	209.6	224.3	239.1	253.3
57.5°	189.8	204.5	217.4	228.5
60°	173.2	182.4	194.8	206.4
62.5°	154.3	164.9	174.6	181.9
65°	135.9	145.1	152.5	158.9
67.5°	120.2	125.7	131.3	138.2
70°	101.3	105.9	112.4	117.5
72.5°	85.2	88.9	92.1	98.1
75°	69.1	72.3	74.2	79.7
77.5°	53.4	56.7	58.0	61.3
80°	41.0	41.5	43.3	46.1
82.5°	28.1	29.0	29.5	31.8
85°	16.1	18.4	18.0	18.9
87.5°	6.9	7.4	8.3	9.2
90°	7.9	6.0	4.2	2.3
92.5°	10.4	10.8	11.1	11.5
95°	24.7	30.4	36.2	42.0
97.5°	91.4	87.7	83.9	80.2
100°	134.4	131.3	128.3	125.2
102.5°	181.7	179.7	177.6	175.6
105°	232.9	231.8	230.8	229.8
107.5°	281.0	280.5	280.0	279.5
110°	331.4	330.9	330.4	329.9

TEST NUMBER: P1013339

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	381.8	380.7	379.7	378.7
115°	430.6	430.1	429.6	429.1
117.5°	476.2	475.5	474.9	474.2
120°	522.0	521.3	520.7	520.0
122.5°	563.8	563.4	563.1	562.7
125°	605.3	604.6	603.9	603.2
127.5°	642.6	642.5	642.3	642.1
130°	680.1	679.9	679.8	679.6
132.5°	714.9	714.6	714.2	713.9
135°	747.8	747.9	748.1	748.3
137.5°	778.8	778.8	778.8	778.8
140°	809.6	809.3	808.9	808.6
142.5°	837.4	836.7	836.0	835.3
145°	864.3	863.8	863.3	862.8
147.5°	887.3	886.2	885.2	884.2
150°	909.9	909.2	908.6	907.9
152.5°	929.2	928.7	928.2	927.7
155°	946.5	946.4	946.2	946.0
157.5°	962.1	962.1	962.1	962.1
160°	974.3	974.8	975.3	975.8
162.5°	986.0	986.7	987.3	988.0
165°	995.4	996.3	997.1	998.0
167.5°	1003.8	1004.6	1005.5	1006.3
170°	1010.1	1011.2	1012.2	1013.2
172.5°	1014.7	1015.8	1016.8	1017.8
175°	1017.8	1018.9	1019.9	1020.9
177.5°	1019.6	1020.7	1021.9	1023.1
180°	1020.9	1020.9	1020.9	1020.9

(END OF REPORT)