

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025182

Luminaire Tested: S124DIP-B1195D590UB35-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025182
REPORT IS A COMBINATION OF REPORTS P995632 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1195D590UB35-4F0-XX-W2A-A
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7730.0 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69			
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	66	64	63	59			
2	94	86	80	75	88	82	76	71	73	69	65	65	62	59	58	56	54	50			
3	86	76	69	63	81	72	65	60	65	60	55	58	54	51	52	49	46	43			
4	79	68	59	53	74	64	57	51	58	52	47	52	47	44	47	43	40	37			
5	72	60	52	46	68	58	50	44	52	46	41	47	42	38	42	38	35	32			
6	67	54	46	40	63	52	44	39	47	41	36	43	37	34	38	34	31	28			
7	62	49	41	36	58	47	40	34	43	37	32	39	34	30	35	31	28	25			
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25	23			
9	54	41	34	28	51	39	32	28	36	30	26	33	28	24	30	26	22	20			
10	50	38	31	26	48	36	29	25	33	27	23	30	25	22	28	24	20	19			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15819	15819	15819	15819
5°	15779	18148	15871	13637
10°	15661	21173	15781	11963
15°	15473	24408	15580	10704
20°	15273	26467	15383	9597
25°	14980	26165	15123	8781
30°	14694	21626	14873	8359
35°	14293	16116	14450	8104
40°	13824	12140	13959	7979
45°	13110	9743	13273	7809
50°	12256	8208	12434	7729
55°	11252	7144	11428	7639
60°	10275	6291	10577	7511
65°	9360	5414	9448	7199
70°	8284	4453	8462	6629
75°	7225	3421	7179	5632
80°	5684	2249	5618	4275
85°	3740	1010	3507	2492

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 20455 cd/sqm

TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.8	2.4
10°-20°	582.7	7.5
20°-30°	925.8	12.0
30°-40°	1028.7	13.3
40°-50°	935.5	12.1
50°-60°	764.5	9.9
60°-70°	545.7	7.1
70°-80°	300.3	3.9
80°-90°	82.7	1.1
90°-100°	25.5	0.3
100°-110°	167.8	2.2
110°-120°	320.5	4.1
120°-130°	406.8	5.3
130°-140°	435.2	5.6
140°-150°	406.9	5.3
150°-160°	328.2	4.2
160°-170°	211.6	2.7
170°-180°	72.9	0.9
0°-30°	1697.3	22.0
0°-40°	2726.0	35.3
0°-60°	4425.9	57.3
0°-90°	5354.6	69.3
90°-120°	513.8	6.6
90°-150°	1762.7	22.8
90°-180°	2375.0	30.7
0°-180°	7730.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1940	1940	1940	1940	1940	
5°	1932	2276	1943	1710	1932	183
15°	1845	3126	1858	1371	1845	521
25°	1684	3319	1700	1114	1684	776
35°	1461	1962	1477	987	1461	913
45°	1165	1101	1180	882	1165	899
55°	820	720	832	770	820	737
65°	511	463	516	616	511	505
75°	251	231	249	381	251	263
85°	51	48	48	119	51	60
90°	2	17	2	17	2	5
95°	32	17	32	17	32	39
105°	173	164	173	164	173	181
115°	323	325	323	325	323	318
125°	454	457	454	457	454	405
135°	563	567	563	567	563	434
145°	649	652	649	652	649	405
155°	711	711	711	711	711	328
165°	750	747	750	747	750	212
175°	768	763	768	763	768	73
180°	768	768	768	768	768	

TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	284.8	285.6	286.3	287.1	287.8	288.2	288.3	288.6	288.9	289.1	289.4
115°	322.7	323.1	323.5	323.8	324.2	324.4	324.3	324.2	324.1	323.9	323.8
117.5°	356.6	357.1	357.6	358.1	358.6	358.9	359.1	359.5	359.8	360.2	360.6
120°	391.0	391.5	392.0	392.5	393.0	393.3	393.2	393.1	393.0	392.8	392.7
122.5°	423.2	423.4	423.7	423.9	424.2	424.3	424.4	424.7	425.0	425.2	425.5
125°	453.6	454.1	454.6	455.1	455.6	455.9	455.8	455.5	455.2	455.0	454.7
127.5°	482.9	483.0	483.1	483.2	483.3	483.4	483.7	484.4	485.0	485.7	486.3
130°	511.0	511.1	511.3	511.4	511.5	511.6	511.8	512.2	512.5	512.9	513.3
132.5°	536.8	537.1	537.3	537.6	537.9	538.0	538.3	538.8	539.3	539.8	540.3
135°	562.7	562.6	562.4	562.3	562.2	562.1	562.4	562.9	563.4	563.9	564.4
137.5°	585.7	585.7	585.7	585.7	585.7	585.7	586.0	586.6	587.3	587.9	588.5
140°	608.0	608.3	608.5	608.8	609.1	609.2	609.3	609.6	609.8	610.1	610.3
142.5°	628.1	628.6	629.1	629.6	630.1	630.4	630.5	630.6	630.7	630.9	631.0
145°	648.8	649.2	649.6	649.9	650.3	650.5	650.5	650.5	650.5	650.5	650.5
147.5°	664.9	665.7	666.4	667.2	667.9	668.3	668.2	668.1	668.0	667.9	667.8
150°	682.7	683.2	683.7	684.2	684.7	685.0	684.9	684.8	684.7	684.5	684.4
152.5°	697.6	698.0	698.4	698.7	699.1	699.3	699.2	698.9	698.7	698.4	698.2
155°	711.4	711.5	711.7	711.8	711.9	712.0	711.8	711.4	711.0	710.6	710.2
157.5°	723.5	723.5	723.5	723.5	723.5	723.5	723.2	722.7	722.2	721.7	721.2
160°	733.8	733.4	733.0	732.7	732.3	732.1	732.0	731.9	731.8	731.6	731.5
162.5°	743.0	742.5	742.0	741.5	741.0	740.7	740.6	740.5	740.4	740.2	740.1
165°	750.4	749.8	749.2	748.5	747.9	747.6	747.6	747.6	747.6	747.6	747.6
167.5°	756.8	756.2	755.5	754.9	754.2	753.9	753.8	753.7	753.6	753.4	753.3
170°	761.9	761.1	760.4	759.6	758.9	758.5	758.6	758.7	758.8	758.9	759.0
172.5°	765.4	764.6	763.8	763.1	762.3	761.9	762.0	762.1	762.2	762.4	762.5
175°	767.7	766.9	766.1	765.4	764.6	764.2	764.3	764.4	764.5	764.7	764.8
177.5°	769.4	768.5	767.6	766.7	765.8	765.4	765.5	765.8	766.0	766.3	766.5
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7

TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	289.3	289.1	289.0	288.9	288.8	289.1	289.6	290.1	290.6	291.1	290.6
115°	324.1	324.3	324.6	324.9	325.0	325.0	325.0	325.0	325.0	325.0	325.0
117.5°	360.5	360.3	360.2	360.1	360.0	360.0	360.0	360.0	360.0	360.0	360.0
120°	393.0	393.2	393.5	393.8	393.9	393.8	393.5	393.2	393.0	392.7	393.0
122.5°	425.6	425.7	425.8	425.9	426.0	425.9	425.6	425.4	425.1	424.9	425.1
125°	455.1	455.5	455.9	456.3	456.5	456.6	456.7	456.8	456.9	457.0	456.9
127.5°	486.2	486.0	485.9	485.8	485.7	485.6	485.5	485.4	485.3	485.2	485.3
130°	513.4	513.6	513.7	513.8	513.9	513.9	513.9	513.9	513.9	513.9	513.9
132.5°	540.4	540.6	540.7	540.8	540.9	540.8	540.7	540.6	540.4	540.3	540.4
135°	564.7	564.9	565.2	565.5	565.6	565.7	566.0	566.2	566.5	566.7	566.5
137.5°	588.8	589.0	589.3	589.6	589.7	589.6	589.5	589.4	589.2	589.1	589.2
140°	610.7	611.1	611.5	611.9	612.1	612.2	612.3	612.4	612.5	612.6	612.5
142.5°	631.3	631.5	631.8	632.1	632.2	632.2	632.2	632.2	632.2	632.2	632.2
145°	650.6	650.8	650.9	651.0	651.1	651.2	651.5	651.8	652.0	652.3	652.0
147.5°	667.9	668.0	668.1	668.2	668.3	668.4	668.5	668.6	668.8	668.9	668.8
150°	684.4	684.4	684.4	684.4	684.4	684.5	684.6	684.7	684.9	685.0	684.9
152.5°	698.4	698.7	698.9	699.2	699.3	699.2	699.1	699.0	698.9	698.8	698.9
155°	710.7	711.2	711.7	712.2	712.5	712.3	711.9	711.6	711.2	710.8	711.2
157.5°	721.8	722.4	723.1	723.7	724.0	723.7	723.1	722.4	721.8	721.2	721.8
160°	732.3	733.0	733.8	734.5	734.9	734.5	733.8	733.0	732.3	731.5	732.3
162.5°	740.9	741.6	742.4	743.1	743.5	743.1	742.2	741.3	740.4	739.5	740.4
165°	748.6	749.6	750.7	751.7	752.2	751.6	750.5	749.3	748.2	747.0	748.2
167.5°	754.5	755.6	756.8	757.9	758.5	757.9	756.6	755.3	754.0	752.7	754.0
170°	760.0	761.0	762.1	763.1	763.6	763.0	761.7	760.4	759.2	757.9	759.2
172.5°	763.5	764.5	765.6	766.6	767.1	766.4	765.0	763.6	762.2	760.8	762.2
175°	766.0	767.1	768.3	769.4	770.0	769.2	767.7	766.2	764.6	763.1	764.6
177.5°	767.5	768.5	769.6	770.6	771.1	770.3	768.8	767.3	765.7	764.2	765.7
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7

TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	290.1	289.6	289.1	288.8	288.9	289.0	289.1	289.3	289.4	289.1	288.9
115°	325.0	325.0	325.0	325.0	324.9	324.6	324.3	324.1	323.8	323.9	324.1
117.5°	360.0	360.0	360.0	360.0	360.1	360.2	360.3	360.5	360.6	360.2	359.8
120°	393.2	393.5	393.8	393.9	393.8	393.5	393.2	393.0	392.7	392.8	393.0
122.5°	425.4	425.6	425.9	426.0	425.9	425.8	425.7	425.6	425.5	425.2	425.0
125°	456.8	456.7	456.6	456.5	456.3	455.9	455.5	455.1	454.7	455.0	455.2
127.5°	485.4	485.5	485.6	485.7	485.8	485.9	486.0	486.2	486.3	485.7	485.0
130°	513.9	513.9	513.9	513.9	513.8	513.7	513.6	513.4	513.3	512.9	512.5
132.5°	540.6	540.7	540.8	540.9	540.8	540.7	540.6	540.4	540.3	539.8	539.3
135°	566.2	566.0	565.7	565.6	565.5	565.2	564.9	564.7	564.4	563.9	563.4
137.5°	589.4	589.5	589.6	589.7	589.6	589.3	589.0	588.8	588.5	587.9	587.3
140°	612.4	612.3	612.2	612.1	611.9	611.5	611.1	610.7	610.3	610.1	609.8
142.5°	632.2	632.2	632.2	632.2	632.1	631.8	631.5	631.3	631.0	630.9	630.7
145°	651.8	651.5	651.2	651.1	651.0	650.9	650.8	650.6	650.5	650.5	650.5
147.5°	668.6	668.5	668.4	668.3	668.2	668.1	668.0	667.9	667.8	667.9	668.0
150°	684.7	684.6	684.5	684.4	684.4	684.4	684.4	684.4	684.4	684.5	684.7
152.5°	699.0	699.1	699.2	699.3	699.2	698.9	698.7	698.4	698.2	698.4	698.7
155°	711.6	711.9	712.3	712.5	712.2	711.7	711.2	710.7	710.2	710.6	711.0
157.5°	722.4	723.1	723.7	724.0	723.7	723.1	722.4	721.8	721.2	721.7	722.2
160°	733.0	733.8	734.5	734.9	734.5	733.8	733.0	732.3	731.5	731.6	731.8
162.5°	741.3	742.2	743.1	743.5	743.1	742.4	741.6	740.9	740.1	740.2	740.4
165°	749.3	750.5	751.6	752.2	751.7	750.7	749.6	748.6	747.6	747.6	747.6
167.5°	755.3	756.6	757.9	758.5	757.9	756.8	755.6	754.5	753.3	753.4	753.6
170°	760.4	761.7	763.0	763.6	763.1	762.1	761.0	760.0	759.0	758.9	758.8
172.5°	763.6	765.0	766.4	767.1	766.6	765.6	764.5	763.5	762.5	762.4	762.2
175°	766.2	767.7	769.2	770.0	769.4	768.3	767.1	766.0	764.8	764.7	764.5
177.5°	767.3	768.8	770.3	771.1	770.6	769.6	768.5	767.5	766.5	766.3	766.0
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7

TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	288.6	288.3	288.2	287.8	287.1	286.3	285.6	284.8	285.6	286.3	287.1
115°	324.2	324.3	324.4	324.2	323.8	323.5	323.1	322.7	323.1	323.5	323.8
117.5°	359.5	359.1	358.9	358.6	358.1	357.6	357.1	356.6	357.1	357.6	358.1
120°	393.1	393.2	393.3	393.0	392.5	392.0	391.5	391.0	391.5	392.0	392.5
122.5°	424.7	424.4	424.3	424.2	423.9	423.7	423.4	423.2	423.4	423.7	423.9
125°	455.5	455.8	455.9	455.6	455.1	454.6	454.1	453.6	454.1	454.6	455.1
127.5°	484.4	483.7	483.4	483.3	483.2	483.1	483.0	482.9	483.0	483.1	483.2
130°	512.2	511.8	511.6	511.5	511.4	511.3	511.1	511.0	511.1	511.3	511.4
132.5°	538.8	538.3	538.0	537.9	537.6	537.3	537.1	536.8	537.1	537.3	537.6
135°	562.9	562.4	562.1	562.2	562.3	562.4	562.6	562.7	562.6	562.4	562.3
137.5°	586.6	586.0	585.7	585.7	585.7	585.7	585.7	585.7	585.7	585.7	585.7
140°	609.6	609.3	609.2	609.1	608.8	608.5	608.3	608.0	608.3	608.5	608.8
142.5°	630.6	630.5	630.4	630.1	629.6	629.1	628.6	628.1	628.6	629.1	629.6
145°	650.5	650.5	650.5	650.3	649.9	649.6	649.2	648.8	649.2	649.6	649.9
147.5°	668.1	668.2	668.3	667.9	667.2	666.4	665.7	664.9	665.7	666.4	667.2
150°	684.8	684.9	685.0	684.7	684.2	683.7	683.2	682.7	683.2	683.7	684.2
152.5°	698.9	699.2	699.3	699.1	698.7	698.4	698.0	697.6	698.0	698.4	698.7
155°	711.4	711.8	712.0	711.9	711.8	711.7	711.5	711.4	711.5	711.7	711.8
157.5°	722.7	723.2	723.5	723.5	723.5	723.5	723.5	723.5	723.5	723.5	723.5
160°	731.9	732.0	732.1	732.3	732.7	733.0	733.4	733.8	733.4	733.0	732.7
162.5°	740.5	740.6	740.7	741.0	741.5	742.0	742.5	743.0	742.5	742.0	741.5
165°	747.6	747.6	747.6	747.9	748.5	749.2	749.8	750.4	749.8	749.2	748.5
167.5°	753.7	753.8	753.9	754.2	754.9	755.5	756.2	756.8	756.2	755.5	754.9
170°	758.7	758.6	758.5	758.9	759.6	760.4	761.1	761.9	761.1	760.4	759.6
172.5°	762.1	762.0	761.9	762.3	763.1	763.8	764.6	765.4	764.6	763.8	763.1
175°	764.4	764.3	764.2	764.6	765.4	766.1	766.9	767.7	766.9	766.1	765.4
177.5°	765.8	765.5	765.4	765.8	766.7	767.6	768.5	769.4	768.5	767.6	766.7
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7

TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9
2.5°	1911.0	1904.5	1907.8	1891.7	1877.2	1856.3	1838.6	1835.4	1832.2	1841.9	1835.4
5°	1856.3	1848.3	1840.2	1821.0	1792.0	1774.4	1748.6	1747.0	1737.4	1722.9	1726.1
7.5°	1796.9	1792.0	1780.8	1750.2	1724.5	1694.0	1673.1	1655.4	1647.4	1634.5	1629.7
10°	1748.6	1731.0	1721.3	1687.6	1657.0	1624.9	1597.6	1584.7	1570.2	1559.0	1551.0
12.5°	1682.7	1677.9	1650.6	1623.3	1597.6	1560.6	1539.7	1502.7	1483.4	1493.1	1489.9
15°	1639.3	1616.8	1610.4	1571.8	1528.5	1504.3	1465.8	1441.7	1433.6	1419.2	1401.5
17.5°	1581.5	1567.0	1544.5	1509.2	1459.3	1425.6	1398.3	1375.8	1366.1	1346.8	1332.4
20°	1526.8	1502.7	1485.1	1452.9	1404.7	1361.3	1327.6	1313.1	1289.0	1272.9	1264.9
22.5°	1477.0	1459.3	1433.6	1385.4	1343.6	1301.8	1261.7	1240.8	1218.3	1208.6	1195.8
25°	1415.9	1387.0	1369.3	1316.3	1271.3	1237.5	1200.6	1173.3	1160.4	1144.3	1141.1
27.5°	1356.5	1329.2	1308.3	1261.7	1207.0	1163.6	1141.1	1121.8	1099.3	1099.3	1091.3
30°	1297.0	1277.7	1245.6	1200.6	1149.2	1107.4	1081.6	1064.0	1055.9	1049.5	1047.9
32.5°	1237.5	1211.8	1192.5	1131.5	1092.9	1054.3	1035.0	1020.6	1010.9	1009.3	1010.9
35°	1176.5	1147.5	1128.3	1073.6	1035.0	999.7	991.6	978.8	974.0	972.4	980.4
37.5°	1112.2	1089.7	1065.6	1020.6	977.2	956.3	940.2	935.4	933.8	943.4	946.6
40°	1052.7	1033.4	1010.9	962.7	930.6	908.1	900.0	895.2	901.6	911.3	916.1
42.5°	996.5	969.1	951.5	908.1	879.1	866.3	856.6	856.6	863.1	874.3	882.4
45°	937.0	916.1	898.4	859.9	834.1	819.7	818.1	819.7	827.7	835.7	845.4
47.5°	879.1	858.2	839.0	806.8	784.3	776.3	774.7	776.3	789.1	800.4	811.6
50°	826.1	803.6	785.9	755.4	737.7	728.1	729.7	737.7	747.3	763.4	777.9
52.5°	763.4	747.3	731.3	704.0	687.9	681.5	686.3	692.7	710.4	721.6	739.3
55°	702.3	687.9	675.0	654.1	641.3	636.5	639.7	649.3	663.8	683.1	704.0
57.5°	646.1	630.0	617.2	602.7	588.2	589.8	591.5	604.3	622.0	639.7	663.8
60°	583.4	573.8	562.5	544.8	538.4	538.4	543.2	557.7	573.8	602.7	623.6
62.5°	527.2	514.3	506.3	495.0	485.4	487.0	498.2	511.1	530.4	554.5	581.8
65°	469.3	454.8	448.4	438.8	435.6	437.2	445.2	464.5	485.4	506.3	532.0
67.5°	405.0	400.2	393.8	384.1	387.3	388.9	397.0	413.1	435.6	456.4	485.4
70°	350.4	340.7	339.1	331.1	331.1	335.9	352.0	363.2	384.1	406.6	437.2
72.5°	292.5	284.5	284.5	278.0	282.9	287.7	295.7	311.8	331.1	353.6	379.3
75°	233.0	229.8	233.0	229.8	229.8	237.9	247.5	260.4	281.3	305.4	326.3
77.5°	180.0	180.0	178.4	183.2	183.2	188.0	200.9	213.8	229.8	249.1	271.6
80°	131.8	131.8	131.8	136.6	141.4	141.4	149.5	165.5	180.0	192.9	213.8
82.5°	90.0	90.0	90.0	93.2	99.6	99.6	109.3	118.9	135.0	146.3	155.9
85°	54.6	54.6	53.0	56.3	57.9	62.7	70.7	77.1	85.2	94.8	104.5
87.5°	24.1	24.1	25.7	27.3	28.9	32.1	35.4	38.6	46.6	49.8	54.6
90°	7.3	8.0	8.5	9.5	10.6	11.6	12.6	13.4	14.2	14.9	15.7
92.5°	7.6	7.5	8.0	9.0	10.1	11.1	12.1	12.9	13.6	14.4	15.1
95°	14.3	12.1	12.2	12.3	12.4	12.5	12.6	13.4	14.2	14.9	15.7
97.5°	71.5	72.9	66.2	52.8	39.4	26.0	12.6	13.2	13.9	14.5	15.2
100°	103.4	104.5	95.7	78.1	60.5	42.9	25.3	23.1	20.9	18.8	16.6
102.5°	138.1	138.9	139.7	141.2	142.7	144.3	145.8	117.1	88.4	59.7	31.0
105°	175.9	176.3	176.6	177.2	177.9	178.5	179.1	180.3	181.4	182.6	183.7
107.5°	211.7	211.9	212.3	213.2	214.1	215.0	215.9	216.5	217.2	217.8	218.5
110°	249.6	249.8	250.2	250.9	251.7	252.4	253.2	253.5	253.7	254.0	254.3

TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	287.8	288.2	288.3	288.6	288.9	289.1	289.4	289.3	289.1	289.0	288.9
115°	324.2	324.4	324.3	324.2	324.1	323.9	323.8	324.1	324.3	324.6	324.9
117.5°	358.6	358.9	359.1	359.5	359.8	360.2	360.6	360.5	360.3	360.2	360.1
120°	393.0	393.3	393.2	393.1	393.0	392.8	392.7	393.0	393.2	393.5	393.8
122.5°	424.2	424.3	424.4	424.7	425.0	425.2	425.5	425.6	425.7	425.8	425.9
125°	455.6	455.9	455.8	455.5	455.2	455.0	454.7	455.1	455.5	455.9	456.3
127.5°	483.3	483.4	483.7	484.4	485.0	485.7	486.3	486.2	486.0	485.9	485.8
130°	511.5	511.6	511.8	512.2	512.5	512.9	513.3	513.4	513.6	513.7	513.8
132.5°	537.9	538.0	538.3	538.8	539.3	539.8	540.3	540.4	540.6	540.7	540.8
135°	562.2	562.1	562.4	562.9	563.4	563.9	564.4	564.7	564.9	565.2	565.5
137.5°	585.7	585.7	586.0	586.6	587.3	587.9	588.5	588.8	589.0	589.3	589.6
140°	609.1	609.2	609.3	609.6	609.8	610.1	610.3	610.7	611.1	611.5	611.9
142.5°	630.1	630.4	630.5	630.6	630.7	630.9	631.0	631.3	631.5	631.8	632.1
145°	650.3	650.5	650.5	650.5	650.5	650.5	650.5	650.6	650.8	650.9	651.0
147.5°	667.9	668.3	668.2	668.1	668.0	667.9	667.8	667.9	668.0	668.1	668.2
150°	684.7	685.0	684.9	684.8	684.7	684.5	684.4	684.4	684.4	684.4	684.4
152.5°	699.1	699.3	699.2	698.9	698.7	698.4	698.2	698.4	698.7	698.9	699.2
155°	711.9	712.0	711.8	711.4	711.0	710.6	710.2	710.7	711.2	711.7	712.2
157.5°	723.5	723.5	723.2	722.7	722.2	721.7	721.2	721.8	722.4	723.1	723.7
160°	732.3	732.1	732.0	731.9	731.8	731.6	731.5	732.3	733.0	733.8	734.5
162.5°	741.0	740.7	740.6	740.5	740.4	740.2	740.1	740.9	741.6	742.4	743.1
165°	747.9	747.6	747.6	747.6	747.6	747.6	747.6	748.6	749.6	750.7	751.7
167.5°	754.2	753.9	753.8	753.7	753.6	753.4	753.3	754.5	755.6	756.8	757.9
170°	758.9	758.5	758.6	758.7	758.8	758.9	759.0	760.0	761.0	762.1	763.1
172.5°	762.3	761.9	762.0	762.1	762.2	762.4	762.5	763.5	764.5	765.6	766.6
175°	764.6	764.2	764.3	764.4	764.5	764.7	764.8	766.0	767.1	768.3	769.4
177.5°	765.8	765.4	765.5	765.8	766.0	766.3	766.5	767.5	768.5	769.6	770.6
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7

TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9
2.5°	1830.6	1829.0	1821.0	1824.2	1814.5	1817.7	1822.6	1824.2	1830.6	1825.8	1824.2
5°	1718.1	1714.9	1710.1	1705.2	1703.6	1710.1	1698.8	1702.0	1705.2	1710.1	1716.5
7.5°	1626.5	1624.9	1620.1	1612.0	1608.8	1605.6	1607.2	1618.5	1616.8	1615.2	1626.5
10°	1542.9	1544.5	1534.9	1533.3	1523.6	1522.0	1523.6	1526.8	1531.7	1538.1	1539.7
12.5°	1456.1	1477.0	1459.3	1452.9	1438.4	1446.5	1449.7	1435.2	1443.3	1448.1	1472.2
15°	1401.5	1391.8	1380.6	1380.6	1374.2	1370.9	1362.9	1374.2	1380.6	1390.2	1387.0
17.5°	1325.9	1309.9	1303.4	1297.0	1298.6	1305.0	1287.4	1313.1	1313.1	1317.9	1309.9
20°	1260.0	1247.2	1239.2	1235.9	1231.1	1227.9	1226.3	1232.7	1242.4	1245.6	1253.6
22.5°	1190.9	1190.9	1178.1	1173.3	1170.0	1165.2	1173.3	1168.4	1174.9	1181.3	1194.2
25°	1133.1	1133.1	1128.3	1121.8	1117.0	1113.8	1118.6	1117.0	1121.8	1129.9	1133.1
27.5°	1086.5	1081.6	1080.0	1078.4	1076.8	1078.4	1076.8	1081.6	1086.5	1088.1	1084.9
30°	1046.3	1041.5	1043.1	1043.1	1044.7	1043.1	1041.5	1046.3	1047.9	1044.7	1046.3
32.5°	1009.3	1009.3	1012.5	1014.1	1014.1	1015.8	1017.4	1014.1	1015.8	1010.9	1012.5
35°	978.8	982.0	985.2	986.8	988.4	986.8	990.0	988.4	985.2	982.0	980.4
37.5°	948.3	951.5	957.9	959.5	964.3	965.9	962.7	962.7	961.1	954.7	951.5
40°	916.1	919.3	927.4	932.2	935.4	940.2	937.0	937.0	930.6	924.1	919.3
42.5°	885.6	892.0	900.0	904.9	911.3	911.3	911.3	908.1	900.0	893.6	888.8
45°	855.0	856.6	867.9	875.9	882.4	882.4	882.4	877.5	872.7	859.9	853.4
47.5°	821.3	826.1	839.0	847.0	853.4	855.0	855.0	850.2	840.6	829.3	821.3
50°	784.3	792.4	806.8	818.1	826.1	829.3	824.5	821.3	810.0	797.2	787.5
52.5°	749.0	758.6	776.3	785.9	797.2	798.8	797.2	792.4	779.5	761.8	753.8
55°	713.6	721.6	740.9	757.0	766.6	769.9	766.6	758.6	742.5	724.8	716.8
57.5°	675.0	686.3	707.2	723.2	734.5	736.1	732.9	724.8	712.0	689.5	678.2
60°	634.8	649.3	670.2	686.3	700.7	702.3	699.1	687.9	671.8	649.3	639.7
62.5°	594.7	605.9	630.0	647.7	659.0	667.0	660.6	649.3	633.2	610.7	596.3
65°	548.1	564.1	585.0	601.1	614.0	615.6	612.3	602.7	585.0	560.9	549.7
67.5°	503.1	514.3	535.2	556.1	560.9	565.7	560.9	551.3	536.8	515.9	499.8
70°	448.4	458.1	483.8	498.2	504.7	509.5	506.3	496.6	483.8	464.5	451.6
72.5°	393.8	401.8	425.9	437.2	450.0	448.4	446.8	440.4	422.7	409.8	401.8
75°	335.9	345.5	361.6	376.1	380.9	380.9	380.9	376.1	364.8	343.9	335.9
77.5°	282.9	287.7	300.5	308.6	313.4	315.0	313.4	305.4	298.9	284.5	279.7
80°	217.0	229.8	239.5	241.1	247.5	247.5	247.5	244.3	237.9	223.4	221.8
82.5°	163.9	167.1	176.8	181.6	184.8	183.2	183.2	176.8	175.2	167.1	163.9
85°	110.9	115.7	114.1	120.5	122.1	118.9	118.9	122.1	114.1	115.7	110.9
87.5°	61.1	61.1	64.3	62.7	69.1	69.1	65.9	67.5	64.3	62.7	61.1
90°	16.1	16.2	16.5	16.7	17.0	17.2	17.0	16.7	16.5	16.2	16.1
92.5°	15.5	15.5	15.5	15.5	15.5	15.5	15.5	15.5	15.5	15.5	15.5
95°	16.1	16.2	16.3	16.4	16.6	16.7	16.6	16.4	16.3	16.2	16.1
97.5°	15.5	15.6	15.7	15.8	16.0	16.1	16.0	15.8	15.7	15.6	15.5
100°	15.5	15.6	15.7	15.8	16.0	16.1	16.0	15.8	15.7	15.6	15.5
102.5°	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7	16.7
105°	184.3	182.0	177.4	172.8	168.2	163.6	168.2	172.8	177.4	182.0	184.3
107.5°	218.8	219.1	219.6	220.1	220.6	221.1	220.6	220.1	219.6	219.1	218.8
110°	254.4	254.6	255.0	255.3	255.7	256.1	255.7	255.3	255.0	254.6	254.4

TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	288.8	289.1	289.6	290.1	290.6	291.1	290.6	290.1	289.6	289.1	288.8
115°	325.0	325.0	325.0	325.0	325.0	325.0	325.0	325.0	325.0	325.0	325.0
117.5°	360.0	360.0	360.0	360.0	360.0	360.0	360.0	360.0	360.0	360.0	360.0
120°	393.9	393.8	393.5	393.2	393.0	392.7	393.0	393.2	393.5	393.8	393.9
122.5°	426.0	425.9	425.6	425.4	425.1	424.9	425.1	425.4	425.6	425.9	426.0
125°	456.5	456.6	456.7	456.8	456.9	457.0	456.9	456.8	456.7	456.6	456.5
127.5°	485.7	485.6	485.5	485.4	485.3	485.2	485.3	485.4	485.5	485.6	485.7
130°	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9	513.9
132.5°	540.9	540.8	540.7	540.6	540.4	540.3	540.4	540.6	540.7	540.8	540.9
135°	565.6	565.7	566.0	566.2	566.5	566.7	566.5	566.2	566.0	565.7	565.6
137.5°	589.7	589.6	589.5	589.4	589.2	589.1	589.2	589.4	589.5	589.6	589.7
140°	612.1	612.2	612.3	612.4	612.5	612.6	612.5	612.4	612.3	612.2	612.1
142.5°	632.2	632.2	632.2	632.2	632.2	632.2	632.2	632.2	632.2	632.2	632.2
145°	651.1	651.2	651.5	651.8	652.0	652.3	652.0	651.8	651.5	651.2	651.1
147.5°	668.3	668.4	668.5	668.6	668.8	668.9	668.8	668.6	668.5	668.4	668.3
150°	684.4	684.5	684.6	684.7	684.9	685.0	684.9	684.7	684.6	684.5	684.4
152.5°	699.3	699.2	699.1	699.0	698.9	698.8	698.9	699.0	699.1	699.2	699.3
155°	712.5	712.3	711.9	711.6	711.2	710.8	711.2	711.6	711.9	712.3	712.5
157.5°	724.0	723.7	723.1	722.4	721.8	721.2	721.8	722.4	723.1	723.7	724.0
160°	734.9	734.5	733.8	733.0	732.3	731.5	732.3	733.0	733.8	734.5	734.9
162.5°	743.5	743.1	742.2	741.3	740.4	739.5	740.4	741.3	742.2	743.1	743.5
165°	752.2	751.6	750.5	749.3	748.2	747.0	748.2	749.3	750.5	751.6	752.2
167.5°	758.5	757.9	756.6	755.3	754.0	752.7	754.0	755.3	756.6	757.9	758.5
170°	763.6	763.0	761.7	760.4	759.2	757.9	759.2	760.4	761.7	763.0	763.6
172.5°	767.1	766.4	765.0	763.6	762.2	760.8	762.2	763.6	765.0	766.4	767.1
175°	770.0	769.2	767.7	766.2	764.6	763.1	764.6	766.2	767.7	769.2	770.0
177.5°	771.1	770.3	768.8	767.3	765.7	764.2	765.7	767.3	768.8	770.3	771.1
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7

TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9
2.5°	1824.2	1833.8	1824.2	1830.6	1833.8	1841.9	1845.1	1859.5	1864.4	1875.6	1875.6
5°	1714.9	1719.7	1721.3	1727.7	1734.2	1750.2	1761.5	1782.4	1806.5	1809.7	1824.2
7.5°	1626.5	1634.5	1647.4	1642.6	1653.8	1677.9	1692.4	1718.1	1742.2	1755.1	1772.7
10°	1547.7	1557.4	1562.2	1567.0	1587.9	1608.8	1631.3	1649.0	1681.1	1700.4	1714.9
12.5°	1483.4	1475.4	1485.1	1502.7	1526.8	1539.7	1570.2	1597.6	1621.7	1642.6	1655.4
15°	1399.9	1406.3	1415.9	1446.5	1452.9	1485.1	1496.3	1526.8	1571.8	1591.1	1607.2
17.5°	1319.5	1340.4	1359.7	1370.9	1390.2	1415.9	1448.1	1481.8	1510.8	1533.3	1552.6
20°	1255.2	1276.1	1287.4	1295.4	1314.7	1350.1	1380.6	1422.4	1459.3	1477.0	1502.7
22.5°	1203.8	1203.8	1219.9	1244.0	1255.2	1289.0	1314.7	1359.7	1399.9	1422.4	1446.5
25°	1139.5	1149.2	1162.0	1182.9	1199.0	1226.3	1263.3	1301.8	1345.2	1364.5	1395.1
27.5°	1086.5	1097.7	1115.4	1120.2	1136.3	1160.4	1199.0	1240.8	1285.8	1306.7	1332.4
30°	1046.3	1052.7	1059.1	1068.8	1083.3	1104.1	1136.3	1173.3	1227.9	1244.0	1276.1
32.5°	1010.9	1014.1	1017.4	1025.4	1033.4	1054.3	1080.0	1120.2	1165.2	1189.3	1218.3
35°	978.8	975.6	977.2	982.0	990.0	998.1	1025.4	1059.1	1100.9	1129.9	1152.4
37.5°	948.3	941.8	940.2	940.2	943.4	953.1	974.0	1002.9	1047.9	1072.0	1094.5
40°	914.5	908.1	904.9	903.2	901.6	908.1	924.1	953.1	988.4	1010.9	1036.6
42.5°	882.4	875.9	867.9	866.3	863.1	866.3	877.5	904.9	935.4	957.9	978.8
45°	850.2	839.0	829.3	822.9	824.5	819.7	827.7	848.6	884.0	898.4	919.3
47.5°	814.9	802.0	789.1	782.7	776.3	779.5	782.7	800.4	830.9	845.4	866.3
50°	781.1	763.4	749.0	740.9	736.1	732.9	736.1	753.8	776.3	789.1	806.8
52.5°	742.5	724.8	710.4	697.5	691.1	686.3	687.9	704.0	724.8	737.7	755.4
55°	707.2	684.7	665.4	649.3	644.5	642.9	641.3	652.5	670.2	683.1	697.5
57.5°	667.0	644.5	623.6	604.3	594.7	593.1	593.1	596.3	618.8	628.4	636.5
60°	626.8	602.7	580.2	562.5	548.1	543.2	541.6	548.1	559.3	569.0	580.2
62.5°	581.8	557.7	530.4	514.3	499.8	487.0	491.8	493.4	509.5	514.3	523.9
65°	538.4	511.1	488.6	462.9	446.8	438.8	435.6	438.8	451.6	453.2	459.7
67.5°	488.6	462.9	435.6	417.9	403.4	388.9	385.7	385.7	392.2	397.0	405.0
70°	440.4	414.7	384.1	364.8	350.4	337.5	332.7	331.1	335.9	339.1	347.2
72.5°	384.1	358.4	335.9	315.0	297.3	287.7	282.9	279.7	284.5	287.7	289.3
75°	324.7	303.8	281.3	260.4	249.1	239.5	233.0	228.2	231.4	231.4	231.4
77.5°	268.4	247.5	229.8	215.4	200.9	189.7	184.8	180.0	181.6	181.6	184.8
80°	208.9	194.5	180.0	167.1	154.3	144.6	141.4	136.6	133.4	131.8	131.8
82.5°	154.3	143.0	130.2	118.9	112.5	102.9	99.6	93.2	93.2	91.6	91.6
85°	102.9	96.4	83.6	75.5	70.7	65.9	62.7	59.5	54.6	54.6	53.0
87.5°	54.6	51.4	48.2	38.6	38.6	33.8	32.1	30.5	25.7	27.3	27.3
90°	15.7	14.9	14.2	13.4	12.6	11.6	10.6	9.5	8.5	8.0	7.3
92.5°	15.1	14.4	13.6	12.9	12.1	11.1	10.1	9.0	8.0	7.5	7.6
95°	15.7	14.9	14.2	13.4	12.6	12.5	12.4	12.3	12.2	12.1	14.3
97.5°	15.2	14.5	13.9	13.2	12.6	26.0	39.4	52.8	66.2	72.9	71.5
100°	16.6	18.8	20.9	23.1	25.3	42.9	60.5	78.1	95.7	104.5	103.4
102.5°	31.0	59.7	88.4	117.1	145.8	144.3	142.7	141.2	139.7	138.9	138.1
105°	183.7	182.6	181.4	180.3	179.1	178.5	177.9	177.2	176.6	176.3	175.9
107.5°	218.5	217.8	217.2	216.5	215.9	215.0	214.1	213.2	212.3	211.9	211.7
110°	254.3	254.0	253.7	253.5	253.2	252.4	251.7	250.9	250.2	249.8	249.6

TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	288.9	289.0	289.1	289.3	289.4	289.1	288.9	288.6	288.3	288.2	287.8
115°	324.9	324.6	324.3	324.1	323.8	323.9	324.1	324.2	324.3	324.4	324.2
117.5°	360.1	360.2	360.3	360.5	360.6	360.2	359.8	359.5	359.1	358.9	358.6
120°	393.8	393.5	393.2	393.0	392.7	392.8	393.0	393.1	393.2	393.3	393.0
122.5°	425.9	425.8	425.7	425.6	425.5	425.2	425.0	424.7	424.4	424.3	424.2
125°	456.3	455.9	455.5	455.1	454.7	455.0	455.2	455.5	455.8	455.9	455.6
127.5°	485.8	485.9	486.0	486.2	486.3	485.7	485.0	484.4	483.7	483.4	483.3
130°	513.8	513.7	513.6	513.4	513.3	512.9	512.5	512.2	511.8	511.6	511.5
132.5°	540.8	540.7	540.6	540.4	540.3	539.8	539.3	538.8	538.3	538.0	537.9
135°	565.5	565.2	564.9	564.7	564.4	563.9	563.4	562.9	562.4	562.1	562.2
137.5°	589.6	589.3	589.0	588.8	588.5	587.9	587.3	586.6	586.0	585.7	585.7
140°	611.9	611.5	611.1	610.7	610.3	610.1	609.8	609.6	609.3	609.2	609.1
142.5°	632.1	631.8	631.5	631.3	631.0	630.9	630.7	630.6	630.5	630.4	630.1
145°	651.0	650.9	650.8	650.6	650.5	650.5	650.5	650.5	650.5	650.5	650.3
147.5°	668.2	668.1	668.0	667.9	667.8	667.9	668.0	668.1	668.2	668.3	667.9
150°	684.4	684.4	684.4	684.4	684.4	684.5	684.7	684.8	684.9	685.0	684.7
152.5°	699.2	698.9	698.7	698.4	698.2	698.4	698.7	698.9	699.2	699.3	699.1
155°	712.2	711.7	711.2	710.7	710.2	710.6	711.0	711.4	711.8	712.0	711.9
157.5°	723.7	723.1	722.4	721.8	721.2	721.7	722.2	722.7	723.2	723.5	723.5
160°	734.5	733.8	733.0	732.3	731.5	731.6	731.8	731.9	732.0	732.1	732.3
162.5°	743.1	742.4	741.6	740.9	740.1	740.2	740.4	740.5	740.6	740.7	741.0
165°	751.7	750.7	749.6	748.6	747.6	747.6	747.6	747.6	747.6	747.6	747.9
167.5°	757.9	756.8	755.6	754.5	753.3	753.4	753.6	753.7	753.8	753.9	754.2
170°	763.1	762.1	761.0	760.0	759.0	758.9	758.8	758.7	758.6	758.5	758.9
172.5°	766.6	765.6	764.5	763.5	762.5	762.4	762.2	762.1	762.0	761.9	762.3
175°	769.4	768.3	767.1	766.0	764.8	764.7	764.5	764.4	764.3	764.2	764.6
177.5°	770.6	769.6	768.5	767.5	766.5	766.3	766.0	765.8	765.5	765.4	765.8
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7

TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1939.9	1939.9	1939.9	1939.9
2.5°	1886.9	1902.9	1917.4	1939.9
5°	1845.1	1867.6	1898.1	1931.9
7.5°	1796.9	1832.2	1872.4	1919.0
10°	1751.9	1792.0	1843.5	1899.7
12.5°	1705.2	1753.5	1809.7	1870.8
15°	1652.2	1700.4	1763.1	1845.1
17.5°	1604.0	1661.8	1729.4	1816.1
20°	1547.7	1602.4	1676.3	1776.0
22.5°	1497.9	1560.6	1642.6	1729.4
25°	1443.3	1497.9	1579.9	1684.3
27.5°	1388.6	1456.1	1534.9	1636.1
30°	1335.6	1391.8	1477.0	1583.1
32.5°	1277.7	1345.2	1424.0	1523.6
35°	1215.0	1279.3	1353.3	1460.9
37.5°	1158.8	1221.5	1297.0	1391.8
40°	1096.1	1162.0	1231.1	1325.9
42.5°	1035.0	1094.5	1163.6	1250.4
45°	975.6	1027.0	1089.7	1165.2
47.5°	914.5	957.9	1015.8	1083.3
50°	848.6	895.2	938.6	994.9
52.5°	787.5	827.7	863.1	909.7
55°	728.1	755.4	784.3	819.7
57.5°	665.4	686.3	707.2	744.1
60°	602.7	622.0	633.2	657.3
62.5°	541.6	549.7	564.1	578.6
65°	474.1	485.4	493.4	511.1
67.5°	413.1	417.9	425.9	437.2
70°	348.8	360.0	363.2	371.3
72.5°	294.1	298.9	302.2	303.8
75°	233.0	237.9	241.1	250.7
77.5°	183.2	181.6	188.0	189.7
80°	135.0	130.2	131.8	138.2
82.5°	88.4	90.0	88.4	88.4
85°	54.6	53.0	49.8	51.4
87.5°	24.1	24.1	22.5	22.5
90°	5.9	4.5	3.1	1.7
92.5°	7.9	8.1	8.4	8.6
95°	18.6	22.9	27.3	31.6
97.5°	68.7	65.9	63.1	60.3
100°	101.1	98.8	96.5	94.2
102.5°	136.6	135.1	133.6	132.1
105°	175.1	174.4	173.6	172.8
107.5°	211.3	210.9	210.5	210.1
110°	249.2	248.8	248.4	248.0



TEST NUMBER: P1025182

CATALOG NUMBER: S124DIP-B1195D590UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	287.1	286.3	285.6	284.8
115°	323.8	323.5	323.1	322.7
117.5°	358.1	357.6	357.1	356.6
120°	392.5	392.0	391.5	391.0
122.5°	423.9	423.7	423.4	423.2
125°	455.1	454.6	454.1	453.6
127.5°	483.2	483.1	483.0	482.9
130°	511.4	511.3	511.1	511.0
132.5°	537.6	537.3	537.1	536.8
135°	562.3	562.4	562.6	562.7
137.5°	585.7	585.7	585.7	585.7
140°	608.8	608.5	608.3	608.0
142.5°	629.6	629.1	628.6	628.1
145°	649.9	649.6	649.2	648.8
147.5°	667.2	666.4	665.7	664.9
150°	684.2	683.7	683.2	682.7
152.5°	698.7	698.4	698.0	697.6
155°	711.8	711.7	711.5	711.4
157.5°	723.5	723.5	723.5	723.5
160°	732.7	733.0	733.4	733.8
162.5°	741.5	742.0	742.5	743.0
165°	748.5	749.2	749.8	750.4
167.5°	754.9	755.5	756.2	756.8
170°	759.6	760.4	761.1	761.9
172.5°	763.1	763.8	764.6	765.4
175°	765.4	766.1	766.9	767.7
177.5°	766.7	767.6	768.5	769.4
180°	767.7	767.7	767.7	767.7

(END OF REPORT)