

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025579

Luminaire Tested: S124DIP-B575D365UB30-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025579
REPORT IS A COMBINATION OF REPORTS P996164 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D365UB30-4F0-XX-W2A-A1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3857.0 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67		
1	102	98	94	90	96	92	89	86	82	79	77	72	71	69	64	62	61	57		
2	93	86	79	74	87	81	75	71	72	68	64	64	61	58	57	54	52	48		
3	85	76	68	62	80	72	65	60	64	59	54	57	53	49	50	47	45	41		
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39	36		
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	41	37	34	31		
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	27		
7	61	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	24		
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24	22		
9	53	41	33	28	50	39	32	27	35	30	25	32	27	24	29	25	22	20		
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7627	7627	7627	7627
5°	7608	8750	7652	6575
10°	7551	10209	7608	5769
15°	7460	11768	7512	5161
20°	7364	12762	7417	4627
25°	7223	12615	7292	4233
30°	7085	10427	7171	4030
35°	6892	7770	6968	3907
40°	6665	5853	6730	3847
45°	6321	4698	6400	3765
50°	5909	3958	5996	3727
55°	5425	3445	5510	3683
60°	4954	3033	5099	3621
65°	4512	2610	4556	3471
70°	3993	2148	4080	3197
75°	3484	1650	3461	2716
80°	2739	1085	2710	2061
85°	1805	486	1688	1201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 9863 cd/sqm

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.0	2.4
10°-20°	281.0	7.3
20°-30°	446.4	11.6
30°-40°	496.0	12.9
40°-50°	451.0	11.7
50°-60°	368.6	9.6
60°-70°	263.1	6.8
70°-80°	144.8	3.8
80°-90°	40.1	1.0
90°-100°	30.0	0.8
100°-110°	89.7	2.3
110°-120°	152.4	4.0
120°-130°	201.0	5.2
130°-140°	225.8	5.9
140°-150°	221.9	5.8
150°-160°	186.6	4.8
160°-170°	124.2	3.2
170°-180°	43.5	1.1
0°-30°	818.4	21.2
0°-40°	1314.4	34.1
0°-60°	2134.0	55.3
0°-90°	2582.0	66.9
90°-120°	272.1	7.1
90°-150°	920.8	23.9
90°-180°	1275.0	33.1
0°-180°	3857.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	935	935	935	935	935	
5°	932	1097	937	824	932	88
15°	890	1507	896	661	890	251
25°	812	1600	820	537	812	374
35°	704	946	712	476	704	440
45°	562	531	569	425	562	433
55°	395	347	401	371	395	355
65°	246	223	249	297	246	243
75°	121	112	120	184	121	127
85°	25	23	23	57	25	29
90°	1	11	1	11	1	3
95°	21	28	21	28	21	23
105°	83	87	83	87	83	88
115°	155	154	155	154	155	153
125°	226	224	226	224	226	201
135°	291	291	291	291	291	225
145°	354	354	354	354	354	221
155°	405	405	405	405	405	186
165°	441	440	441	440	441	124
175°	459	457	459	457	459	44
180°	460	460	460	460	460	

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	935.3	944.6	948.5	951.6	961.7	964.8	965.6	970.2	974.1	974.9	974.9
5°	931.5	946.2	957.8	968.7	984.9	991.9	1000.4	1009.7	1022.1	1029.9	1033.8
7.5°	925.3	947.0	964.8	983.4	1005.9	1019.8	1027.6	1052.4	1069.4	1083.4	1100.4
10°	916.0	943.9	969.4	996.6	1028.3	1045.4	1062.4	1092.6	1116.7	1143.8	1165.5
12.5°	902.0	938.4	969.4	1007.4	1046.9	1067.1	1087.2	1139.9	1167.8	1191.8	1230.6
15°	889.6	926.0	970.2	1009.0	1057.8	1088.0	1117.4	1151.5	1195.7	1247.6	1284.8
17.5°	875.7	921.4	962.5	1016.7	1071.0	1099.6	1123.6	1176.3	1238.3	1289.5	1323.6
20°	856.3	902.8	957.0	1014.4	1078.7	1101.2	1132.9	1203.5	1259.3	1309.6	1365.4
22.5°	833.8	888.1	945.4	1000.4	1067.1	1114.3	1149.2	1211.2	1278.6	1336.8	1399.5
25°	812.1	871.0	921.4	996.6	1067.1	1098.8	1138.4	1212.0	1285.6	1356.1	1420.4
27.5°	788.9	843.9	912.1	971.8	1051.6	1086.4	1129.1	1209.7	1287.9	1358.4	1427.4
30°	763.3	822.2	878.8	949.3	1026.8	1071.7	1111.2	1198.8	1278.6	1352.3	1416.6
32.5°	734.6	790.4	850.9	917.5	998.9	1044.6	1094.2	1184.1	1269.3	1332.9	1382.5
35°	704.4	761.0	813.7	881.9	965.6	1011.3	1059.3	1158.5	1243.0	1294.9	1323.6
37.5°	671.1	724.6	776.5	843.9	927.6	976.4	1025.2	1121.3	1201.1	1244.5	1236.8
40°	639.3	687.4	735.4	799.0	886.5	938.4	981.1	1077.9	1147.7	1166.3	1140.7
42.5°	602.9	644.0	690.5	755.6	840.8	889.6	943.1	1031.4	1083.4	1075.6	1032.2
45°	561.8	598.2	644.7	706.0	792.8	843.1	888.1	971.8	1009.7	990.4	911.3
47.5°	522.3	557.9	595.9	657.1	741.6	784.2	829.9	905.1	926.8	885.7	806.7
50°	479.7	509.1	548.6	606.8	685.8	730.8	768.7	829.2	836.9	786.6	704.4
52.5°	438.6	463.4	501.4	558.7	632.3	668.0	705.2	758.7	752.5	700.5	621.5
55°	395.2	418.5	453.3	506.0	571.1	605.2	637.0	684.3	671.1	617.6	548.6
57.5°	358.8	375.1	409.2	458.0	511.5	548.6	575.8	613.0	592.8	539.4	475.0
60°	316.9	337.1	365.8	405.3	458.0	482.8	506.8	531.6	517.7	466.5	409.2
62.5°	279.0	294.5	319.3	357.2	398.3	420.8	446.4	461.9	447.9	400.6	352.6
65°	246.4	258.8	278.2	309.2	348.7	367.3	382.0	396.8	385.1	341.0	306.1
67.5°	210.8	221.6	237.9	262.7	296.0	309.2	323.1	333.2	320.0	290.6	256.5
70°	179.0	186.8	202.3	220.9	244.1	256.5	268.1	278.2	266.6	241.8	216.2
72.5°	146.5	152.7	166.6	179.8	200.7	209.2	217.8	225.5	221.6	198.4	177.5
75°	120.9	123.2	132.5	143.4	156.5	165.8	172.0	176.7	173.6	155.0	141.8
77.5°	91.4	94.5	101.5	110.0	121.7	127.1	131.0	135.6	131.7	117.0	107.7
80°	66.6	67.4	71.3	79.0	86.8	87.6	91.4	97.6	95.3	85.2	78.3
82.5°	42.6	44.9	46.5	51.1	56.6	58.1	60.4	62.0	61.2	55.0	52.7
85°	24.8	24.8	26.3	29.4	31.0	33.3	34.1	34.9	36.4	32.5	30.2
87.5°	10.8	11.6	11.6	12.4	13.9	13.9	14.7	15.5	16.3	15.5	13.2
90°	1.1	2.0	2.8	3.7	4.6	5.0	5.3	5.9	6.6	7.2	7.8
92.5°	9.2	10.2	11.3	12.3	13.4	13.9	14.1	14.5	14.8	15.2	15.6
95°	21.3	22.0	22.7	23.4	24.1	24.5	24.8	25.3	25.9	26.4	27.0
97.5°	34.1	34.7	35.4	36.0	36.7	37.0	37.3	37.9	38.6	39.2	39.8
100°	49.8	50.1	50.4	50.7	51.0	51.2	51.6	52.3	53.0	53.7	54.4
102.5°	66.1	66.2	66.3	66.4	66.5	66.5	66.8	67.4	68.1	68.7	69.3
105°	82.8	82.9	83.0	83.1	83.2	83.2	83.4	83.7	84.0	84.3	84.6
107.5°	100.2	100.3	100.4	100.5	100.6	100.6	100.6	100.7	100.8	100.8	100.9
110°	118.0	118.2	118.3	118.5	118.6	118.7	118.7	118.6	118.5	118.4	118.3

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	136.5	136.5	136.5	136.5	136.5	136.5	136.4	136.3	136.1	136.0	135.8
115°	155.0	155.0	155.0	155.0	155.0	155.0	154.9	154.7	154.6	154.4	154.2
117.5°	172.4	172.4	172.4	172.4	172.4	172.4	172.4	172.3	172.2	172.1	172.0
120°	189.8	190.1	190.4	190.7	191.0	191.2	191.1	190.8	190.6	190.3	190.1
122.5°	207.9	208.0	208.1	208.2	208.3	208.3	208.3	208.2	208.1	208.0	207.9
125°	225.7	225.7	225.7	225.7	225.7	225.7	225.7	225.6	225.5	225.4	225.3
127.5°	241.7	241.9	242.1	242.4	242.6	242.7	242.6	242.5	242.3	242.2	242.0
130°	258.7	258.9	259.2	259.4	259.7	259.8	259.8	259.8	259.8	259.8	259.8
132.5°	276.1	276.3	276.5	276.6	276.8	276.9	276.9	276.8	276.7	276.6	276.5
135°	291.1	291.6	292.0	292.5	293.0	293.2	293.2	293.2	293.2	293.2	293.2
137.5°	307.8	308.0	308.2	308.5	308.7	308.8	308.9	309.0	309.2	309.3	309.5
140°	324.5	324.7	324.8	325.0	325.1	325.2	325.2	325.2	325.2	325.2	325.2
142.5°	339.8	340.0	340.1	340.3	340.4	340.5	340.5	340.4	340.3	340.2	340.1
145°	353.6	353.9	354.2	354.5	354.8	355.0	355.0	355.1	355.2	355.3	355.4
147.5°	367.8	368.2	368.6	369.0	369.4	369.6	369.6	369.5	369.4	369.4	369.3
150°	380.6	380.9	381.3	381.6	381.9	382.1	382.1	382.1	382.1	382.1	382.1
152.5°	392.7	392.9	393.0	393.2	393.3	393.4	393.4	393.5	393.6	393.7	393.8
155°	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.1	405.0	404.9	404.8
157.5°	415.8	415.6	415.5	415.3	415.2	415.1	415.1	415.1	415.1	415.1	415.1
160°	425.1	425.0	424.9	424.8	424.7	424.7	424.7	424.6	424.5	424.4	424.3
162.5°	433.6	433.4	433.1	432.9	432.6	432.5	432.5	432.4	432.3	432.3	432.2
165°	441.0	440.8	440.6	440.3	440.1	440.0	439.9	439.8	439.6	439.5	439.3
167.5°	447.1	446.8	446.5	446.2	445.9	445.7	445.7	445.7	445.7	445.7	445.7
170°	452.1	451.7	451.3	450.9	450.5	450.3	450.3	450.4	450.5	450.5	450.6
172.5°	455.6	455.3	455.0	454.7	454.4	454.2	454.2	454.2	454.2	454.2	454.2
175°	458.8	458.4	458.0	457.6	457.2	457.0	457.0	456.9	456.8	456.8	456.7
177.5°	460.2	459.8	459.4	459.1	458.7	458.5	458.5	458.5	458.5	458.5	458.5
180°	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	977.2	991.1	997.3	998.9	1007.4	1002.0	1004.3	1003.5	1009.7	1010.5	1010.5
5°	1048.5	1064.8	1070.2	1077.9	1089.5	1092.6	1090.3	1095.0	1103.5	1097.3	1106.6
7.5°	1123.6	1141.5	1153.9	1170.9	1174.8	1184.9	1191.1	1196.5	1198.0	1198.8	1200.4
10°	1193.4	1215.9	1232.9	1261.6	1267.8	1273.2	1300.3	1289.5	1303.4	1298.8	1300.3
12.5°	1250.0	1294.1	1308.1	1356.1	1360.8	1379.4	1377.8	1394.9	1398.0	1404.2	1398.0
15°	1324.4	1375.5	1398.0	1425.1	1440.6	1462.3	1466.2	1489.4	1498.7	1507.2	1498.7
17.5°	1392.5	1419.7	1477.0	1498.7	1508.8	1520.4	1549.9	1558.4	1572.3	1566.9	1582.4
20°	1426.6	1465.4	1525.8	1563.0	1578.5	1589.4	1614.2	1627.4	1632.8	1632.8	1634.3
22.5°	1456.9	1512.7	1557.6	1600.2	1614.2	1621.9	1636.6	1646.7	1649.0	1650.6	1652.1
25°	1484.0	1534.4	1570.8	1594.8	1600.2	1600.2	1608.8	1602.6	1592.5	1600.2	1604.9
27.5°	1484.0	1519.6	1535.9	1544.4	1544.4	1523.5	1511.1	1485.5	1463.8	1457.6	1471.6
30°	1459.2	1475.5	1453.0	1432.1	1415.8	1401.8	1353.0	1314.3	1306.5	1301.1	1322.0
32.5°	1401.8	1380.9	1336.8	1276.3	1252.3	1220.5	1182.5	1153.1	1135.3	1129.1	1124.4
35°	1300.3	1246.1	1188.7	1107.4	1090.3	1050.0	998.1	976.4	947.0	946.2	956.3
37.5°	1189.5	1105.8	1043.8	966.3	942.3	899.7	850.9	828.4	808.3	792.8	811.4
40°	1060.1	987.3	892.7	829.2	795.1	772.6	731.5	706.7	697.4	689.7	701.3
42.5°	939.2	859.4	785.8	720.7	692.8	667.2	640.1	616.1	609.1	608.3	616.8
45°	819.1	740.8	672.6	616.8	599.0	583.5	557.2	550.2	538.6	530.8	534.7
47.5°	723.0	642.4	585.8	543.2	527.7	514.6	497.5	485.9	475.8	472.7	477.4
50°	628.5	574.2	516.1	480.5	468.8	456.4	443.3	432.4	427.8	424.7	427.8
52.5°	552.5	494.4	454.9	426.2	414.6	405.3	396.0	391.3	385.1	386.7	389.8
55°	484.3	433.2	399.9	378.9	372.0	368.1	356.5	351.0	348.7	347.2	348.7
57.5°	420.0	382.8	358.0	340.2	330.9	328.6	319.3	319.3	316.9	314.6	315.4
60°	368.9	337.1	313.1	299.1	297.6	293.7	287.5	286.7	281.3	283.6	284.4
62.5°	316.9	291.4	275.1	266.6	261.2	259.6	255.7	255.0	252.6	253.4	251.9
65°	275.9	255.0	238.7	231.7	229.4	228.6	225.5	223.2	221.6	223.2	221.6
67.5°	234.8	220.9	208.5	201.5	198.4	197.6	195.3	193.7	194.5	192.2	193.7
70°	196.1	182.1	174.4	170.5	168.9	166.6	166.6	166.6	166.6	165.1	164.3
72.5°	165.1	151.1	145.7	143.4	141.8	141.0	138.7	139.5	138.7	137.9	141.0
75°	131.0	122.4	117.0	114.7	116.2	113.9	111.6	113.1	110.8	111.6	114.7
77.5°	99.2	95.3	92.2	90.7	89.1	87.6	87.6	86.0	86.0	86.0	86.0
80°	72.1	71.3	65.9	65.1	65.1	63.5	63.5	63.5	63.5	62.8	63.5
82.5°	48.0	47.3	45.7	44.9	43.4	44.2	44.2	42.6	42.6	41.8	42.6
85°	27.9	27.9	26.3	25.6	24.8	25.6	24.0	23.2	24.0	23.2	24.0
87.5°	13.2	11.6	12.4	11.6	10.1	10.8	9.3	10.1	9.3	8.5	10.1
90°	8.3	8.8	9.3	9.8	10.0	10.1	10.2	10.4	10.5	10.7	10.5
92.5°	15.8	16.1	16.3	16.6	16.7	16.7	16.8	16.9	17.0	17.1	17.0
95°	27.2	27.5	27.7	28.0	28.1	28.1	28.1	28.1	28.1	28.1	28.1
97.5°	40.1	40.4	40.7	41.0	41.2	41.2	41.2	41.2	41.2	41.2	41.2
100°	54.6	54.7	54.9	55.0	55.1	55.1	55.1	55.1	55.1	55.1	55.1
102.5°	69.5	69.8	70.0	70.3	70.4	70.4	70.5	70.6	70.6	70.7	70.6
105°	84.8	85.1	85.3	85.6	85.7	85.8	86.0	86.3	86.5	86.7	86.5
107.5°	101.2	101.6	101.9	102.2	102.4	102.4	102.3	102.2	102.1	102.0	102.1
110°	118.1	118.0	117.8	117.7	117.6	117.7	118.0	118.2	118.5	118.7	118.5

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	135.8	135.8	135.8	135.8	135.8	135.8	135.8	135.8	135.8	135.8	135.8
115°	154.1	154.1	154.0	153.9	153.9	153.9	153.8	153.7	153.6	153.5	153.6
117.5°	171.8	171.5	171.3	171.0	170.9	170.8	170.6	170.3	170.1	169.9	170.1
120°	189.7	189.3	189.0	188.6	188.4	188.5	188.6	188.8	188.9	189.1	188.9
122.5°	207.7	207.4	207.2	206.9	206.8	206.6	206.2	205.9	205.5	205.1	205.5
125°	225.1	225.0	224.8	224.7	224.6	224.5	224.4	224.2	224.1	223.9	224.1
127.5°	241.8	241.7	241.5	241.4	241.3	241.3	241.2	241.1	241.1	241.0	241.1
130°	259.6	259.5	259.3	259.2	259.1	258.9	258.6	258.3	258.0	257.7	258.0
132.5°	276.3	276.2	276.0	275.9	275.8	275.8	275.7	275.6	275.5	275.4	275.5
135°	293.0	292.9	292.7	292.6	292.5	292.4	292.1	291.9	291.6	291.4	291.6
137.5°	309.3	309.1	308.8	308.6	308.5	308.5	308.6	308.7	308.7	308.8	308.7
140°	325.1	325.0	324.9	324.8	324.8	324.8	324.7	324.6	324.6	324.5	324.6
142.5°	340.1	340.1	340.1	340.1	340.1	340.1	340.1	340.1	340.1	340.1	340.1
145°	355.3	355.2	355.1	355.0	355.0	354.9	354.7	354.4	354.2	354.0	354.2
147.5°	369.2	369.1	369.0	368.9	368.9	368.9	368.8	368.7	368.6	368.5	368.6
150°	382.1	382.1	382.1	382.1	382.1	382.1	382.0	381.9	381.8	381.7	381.8
152.5°	394.0	394.2	394.5	394.7	394.8	394.7	394.5	394.2	394.0	393.8	394.0
155°	405.1	405.4	405.7	406.0	406.2	406.0	405.7	405.4	405.1	404.8	405.1
157.5°	415.3	415.6	415.8	416.1	416.2	416.1	415.8	415.6	415.3	415.1	415.3
160°	424.5	424.8	425.0	425.3	425.4	425.2	424.8	424.4	424.0	423.6	424.0
162.5°	432.7	433.1	433.6	434.1	434.3	434.1	433.7	433.3	432.9	432.5	432.9
165°	439.8	440.2	440.7	441.2	441.4	441.2	440.9	440.6	440.3	440.0	440.3
167.5°	446.2	446.6	447.1	447.6	447.8	447.6	447.1	446.6	446.2	445.7	446.2
170°	451.1	451.6	452.1	452.6	452.8	452.5	452.0	451.4	450.9	450.3	450.9
172.5°	454.8	455.3	455.9	456.4	456.7	456.4	455.9	455.3	454.8	454.2	454.8
175°	457.3	457.8	458.4	458.9	459.2	458.9	458.4	457.8	457.3	456.7	457.3
177.5°	459.0	459.6	460.1	460.6	460.9	460.6	460.0	459.3	458.7	458.1	458.7
180°	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	1009.0	1006.6	1003.5	1003.5	999.7	999.7	993.5	982.6	973.3	970.2	971.8
5°	1095.0	1095.7	1091.1	1087.2	1080.3	1074.8	1064.8	1045.4	1039.2	1026.8	1018.3
7.5°	1193.4	1190.3	1181.8	1175.6	1174.0	1161.6	1139.9	1116.7	1098.1	1085.7	1067.9
10°	1304.2	1291.8	1279.4	1275.5	1266.2	1245.3	1220.5	1194.9	1169.4	1142.2	1112.0
12.5°	1397.2	1373.2	1372.4	1363.1	1345.3	1333.7	1304.2	1267.8	1223.6	1193.4	1159.3
15°	1497.2	1474.7	1456.1	1439.0	1430.5	1396.4	1371.6	1325.9	1273.2	1240.7	1217.4
17.5°	1568.5	1558.4	1526.6	1518.9	1507.2	1467.7	1428.2	1383.2	1337.5	1291.8	1229.0
20°	1625.8	1619.6	1598.7	1587.8	1569.2	1538.2	1490.2	1438.3	1385.6	1320.5	1261.6
22.5°	1650.6	1642.8	1625.8	1616.5	1604.9	1578.5	1537.5	1478.6	1409.6	1351.5	1288.7
25°	1601.8	1615.7	1611.1	1607.2	1602.6	1587.1	1556.1	1504.1	1436.7	1370.8	1292.6
27.5°	1491.7	1515.8	1539.0	1542.1	1549.9	1556.1	1543.7	1506.5	1449.9	1380.1	1294.1
30°	1343.7	1354.6	1401.8	1415.8	1426.6	1466.2	1489.4	1480.1	1436.7	1373.9	1294.9
32.5°	1153.9	1182.5	1230.6	1263.9	1293.4	1337.5	1398.0	1422.0	1406.5	1355.4	1277.1
35°	974.1	1008.2	1064.0	1106.6	1136.0	1198.8	1270.1	1322.0	1341.4	1315.8	1246.1
37.5°	826.8	867.9	917.5	933.8	967.9	1045.4	1143.8	1215.9	1263.1	1265.5	1211.2
40°	716.0	737.0	776.5	801.3	834.6	899.7	995.8	1091.1	1162.4	1186.4	1157.7
42.5°	622.3	638.5	668.0	698.2	728.4	778.0	866.4	955.5	1051.6	1099.6	1098.8
45°	547.9	564.9	585.1	609.9	630.8	684.3	754.0	845.4	928.4	1002.8	1021.4
47.5°	482.8	497.5	522.3	533.2	547.1	597.5	657.9	743.2	829.2	914.4	936.1
50°	434.7	447.1	464.2	471.2	486.7	523.9	573.4	642.4	737.7	816.0	856.3
52.5°	391.3	400.6	413.8	419.2	430.1	458.0	502.9	557.2	636.2	716.8	773.4
55°	354.1	360.3	369.6	375.8	383.6	408.4	441.7	490.5	558.7	628.5	683.5
57.5°	319.3	323.9	333.2	336.3	342.5	361.9	385.1	426.2	489.0	551.0	604.4
60°	286.7	289.8	295.2	302.2	306.9	320.0	341.7	375.8	426.2	482.8	526.2
62.5°	255.7	260.4	261.9	265.0	268.9	281.3	298.3	323.1	367.3	413.8	459.5
65°	224.0	227.8	230.9	231.7	235.6	244.9	260.4	282.1	310.7	351.0	393.7
67.5°	194.5	196.8	198.4	201.5	205.4	210.0	222.4	238.7	265.0	297.6	331.7
70°	167.4	167.4	169.7	170.5	175.1	180.6	186.0	201.5	224.7	251.1	274.3
72.5°	137.9	141.8	141.0	144.9	144.1	148.0	155.0	165.1	182.1	203.0	225.5
75°	112.4	114.7	114.7	114.7	116.2	119.3	123.2	132.5	145.7	162.7	175.9
77.5°	87.6	89.1	89.1	89.1	89.9	93.0	96.9	103.1	112.4	122.4	130.2
80°	62.8	64.3	64.3	65.9	65.9	66.6	70.5	73.6	78.3	86.0	93.8
82.5°	42.6	43.4	44.9	44.9	44.2	45.7	46.5	49.6	54.2	55.8	61.2
85°	23.2	24.0	24.8	24.8	25.6	27.1	26.3	29.4	29.4	32.5	34.1
87.5°	9.3	10.8	10.8	10.1	10.8	10.8	10.8	12.4	13.2	13.9	13.2
90°	10.4	10.2	10.1	10.0	9.8	9.3	8.8	8.3	7.8	7.2	6.6
92.5°	16.9	16.8	16.7	16.7	16.6	16.3	16.1	15.8	15.6	15.2	14.8
95°	28.1	28.1	28.1	28.1	28.0	27.7	27.5	27.2	27.0	26.4	25.9
97.5°	41.2	41.2	41.2	41.2	41.0	40.7	40.4	40.1	39.8	39.2	38.6
100°	55.1	55.1	55.1	55.1	55.0	54.9	54.7	54.6	54.4	53.7	53.0
102.5°	70.6	70.5	70.4	70.4	70.3	70.0	69.8	69.5	69.3	68.7	68.1
105°	86.3	86.0	85.8	85.7	85.6	85.3	85.1	84.8	84.6	84.3	84.0
107.5°	102.2	102.3	102.4	102.4	102.2	101.9	101.6	101.2	100.9	100.8	100.8
110°	118.2	118.0	117.7	117.6	117.7	117.8	118.0	118.1	118.3	118.4	118.5

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	135.8	135.8	135.8	135.8	135.8	135.8	135.8	135.8	135.8	136.0	136.1
115°	153.7	153.8	153.9	153.9	153.9	154.0	154.1	154.1	154.2	154.4	154.6
117.5°	170.3	170.6	170.8	170.9	171.0	171.3	171.5	171.8	172.0	172.1	172.2
120°	188.8	188.6	188.5	188.4	188.6	189.0	189.3	189.7	190.1	190.3	190.6
122.5°	205.9	206.2	206.6	206.8	206.9	207.2	207.4	207.7	207.9	208.0	208.1
125°	224.2	224.4	224.5	224.6	224.7	224.8	225.0	225.1	225.3	225.4	225.5
127.5°	241.1	241.2	241.3	241.3	241.4	241.5	241.7	241.8	242.0	242.2	242.3
130°	258.3	258.6	258.9	259.1	259.2	259.3	259.5	259.6	259.8	259.8	259.8
132.5°	275.6	275.7	275.8	275.8	275.9	276.0	276.2	276.3	276.5	276.6	276.7
135°	291.9	292.1	292.4	292.5	292.6	292.7	292.9	293.0	293.2	293.2	293.2
137.5°	308.7	308.6	308.5	308.5	308.6	308.8	309.1	309.3	309.5	309.3	309.2
140°	324.6	324.7	324.8	324.8	324.8	324.9	325.0	325.1	325.2	325.2	325.2
142.5°	340.1	340.1	340.1	340.1	340.1	340.1	340.1	340.1	340.1	340.2	340.3
145°	354.4	354.7	354.9	355.0	355.0	355.1	355.2	355.3	355.4	355.3	355.2
147.5°	368.7	368.8	368.9	368.9	368.9	369.0	369.1	369.2	369.3	369.4	369.4
150°	381.9	382.0	382.1	382.1	382.1	382.1	382.1	382.1	382.1	382.1	382.1
152.5°	394.2	394.5	394.7	394.8	394.7	394.5	394.2	394.0	393.8	393.7	393.6
155°	405.4	405.7	406.0	406.2	406.0	405.7	405.4	405.1	404.8	404.9	405.0
157.5°	415.6	415.8	416.1	416.2	416.1	415.8	415.6	415.3	415.1	415.1	415.1
160°	424.4	424.8	425.2	425.4	425.3	425.0	424.8	424.5	424.3	424.4	424.5
162.5°	433.3	433.7	434.1	434.3	434.1	433.6	433.1	432.7	432.2	432.3	432.3
165°	440.6	440.9	441.2	441.4	441.2	440.7	440.2	439.8	439.3	439.5	439.6
167.5°	446.6	447.1	447.6	447.8	447.6	447.1	446.6	446.2	445.7	445.7	445.7
170°	451.4	452.0	452.5	452.8	452.6	452.1	451.6	451.1	450.6	450.5	450.5
172.5°	455.3	455.9	456.4	456.7	456.4	455.9	455.3	454.8	454.2	454.2	454.2
175°	457.8	458.4	458.9	459.2	458.9	458.4	457.8	457.3	456.7	456.8	456.8
177.5°	459.3	460.0	460.6	460.9	460.6	460.1	459.6	459.0	458.5	458.5	458.5
180°	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	964.8	961.7	959.4	959.4	952.4	945.4	941.5	940.0	938.4	932.2	923.7
5°	1004.3	994.2	987.3	980.3	968.7	956.3	943.9	936.9	926.8	912.9	902.8
7.5°	1048.5	1024.5	1016.7	1008.2	984.9	964.0	947.0	932.2	916.0	898.1	880.3
10°	1085.7	1060.1	1043.1	1028.3	998.1	970.2	944.6	922.9	902.0	878.8	857.1
12.5°	1121.3	1084.9	1067.1	1045.4	1013.6	973.3	940.0	912.9	881.9	857.8	831.5
15°	1170.9	1109.7	1080.3	1066.3	1023.7	976.4	936.1	895.8	870.2	833.8	810.6
17.5°	1178.7	1129.1	1109.7	1074.1	1022.9	969.4	922.9	882.6	843.9	811.4	781.1
20°	1205.8	1140.7	1109.7	1087.2	1019.8	965.6	914.4	862.5	825.3	790.4	756.3
22.5°	1222.8	1149.2	1116.7	1081.0	1016.7	951.6	891.2	846.2	800.5	764.9	737.7
25°	1218.2	1144.6	1108.1	1074.8	996.6	931.5	877.2	819.9	777.3	738.5	702.9
27.5°	1215.9	1132.9	1094.2	1057.0	983.4	915.2	847.0	800.5	753.2	708.3	681.9
30°	1209.7	1118.2	1073.3	1033.0	956.3	885.0	826.8	772.6	725.3	684.3	649.4
32.5°	1188.7	1093.4	1050.0	1006.6	926.8	855.5	796.6	746.3	699.0	656.4	623.0
35°	1160.8	1064.0	1016.7	971.0	891.2	819.1	764.9	712.2	668.0	626.9	595.1
37.5°	1132.9	1029.9	985.7	933.0	859.4	784.2	728.4	681.2	640.1	597.5	562.6
40°	1092.6	989.6	940.8	895.8	809.8	739.3	688.1	645.5	605.2	564.9	535.5
42.5°	1037.6	945.4	895.0	845.4	764.9	695.1	645.5	607.5	569.6	536.3	503.7
45°	981.8	891.9	847.0	802.8	715.3	649.4	603.7	568.8	537.0	500.6	474.3
47.5°	914.4	838.5	793.5	750.1	667.2	601.3	559.5	527.0	497.5	467.3	442.5
50°	845.4	779.6	738.5	693.6	614.5	554.8	513.8	486.7	462.6	434.0	413.8
52.5°	771.1	713.7	678.8	635.4	565.7	510.7	468.8	441.7	421.6	400.6	382.8
55°	692.0	650.2	613.0	578.1	512.2	462.6	425.4	401.4	387.5	368.1	352.6
57.5°	620.7	580.4	557.9	518.4	461.1	412.3	382.8	362.7	346.4	334.8	322.4
60°	546.3	513.8	489.0	460.3	409.9	368.9	337.9	326.2	309.2	300.7	295.2
62.5°	475.0	451.8	428.5	406.8	361.9	323.1	299.9	285.2	275.1	266.6	261.9
65°	407.6	385.9	369.6	350.3	313.1	282.1	260.4	248.8	238.7	236.4	230.9
67.5°	341.7	332.4	314.6	299.1	267.4	243.3	227.1	212.3	206.9	204.6	199.9
70°	285.9	275.1	261.2	248.0	224.0	203.0	188.3	182.9	175.1	174.4	168.9
72.5°	235.6	222.4	212.3	202.3	184.4	165.8	158.1	150.3	146.5	143.4	141.0
75°	186.8	177.5	170.5	162.0	146.5	134.1	123.2	120.1	117.8	117.0	115.5
77.5°	139.5	133.3	130.2	121.7	110.8	100.0	95.3	90.7	90.7	89.1	89.9
80°	99.2	95.3	91.4	86.8	77.5	72.8	69.0	65.9	64.3	63.5	64.3
82.5°	62.8	60.4	59.7	56.6	50.4	48.0	44.9	42.6	42.6	42.6	42.6
85°	34.9	34.9	34.9	30.2	27.9	25.6	24.0	23.2	23.2	23.2	24.0
87.5°	14.7	14.7	12.4	12.4	11.6	10.1	9.3	9.3	10.1	10.1	10.8
90°	5.9	5.3	5.0	4.6	3.7	2.8	2.0	1.1	2.0	2.8	3.7
92.5°	14.5	14.1	13.9	13.4	12.3	11.3	10.2	9.2	10.2	11.3	12.3
95°	25.3	24.8	24.5	24.1	23.4	22.7	22.0	21.3	22.0	22.7	23.4
97.5°	37.9	37.3	37.0	36.7	36.0	35.4	34.7	34.1	34.7	35.4	36.0
100°	52.3	51.6	51.2	51.0	50.7	50.4	50.1	49.8	50.1	50.4	50.7
102.5°	67.4	66.8	66.5	66.5	66.4	66.3	66.2	66.1	66.2	66.3	66.4
105°	83.7	83.4	83.2	83.2	83.1	83.0	82.9	82.8	82.9	83.0	83.1
107.5°	100.7	100.6	100.6	100.6	100.5	100.4	100.3	100.2	100.3	100.4	100.5
110°	118.6	118.7	118.7	118.6	118.5	118.3	118.2	118.0	118.2	118.3	118.5

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	136.3	136.4	136.5	136.5	136.5	136.5	136.5	136.5	136.5	136.5	136.5
115°	154.7	154.9	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0
117.5°	172.3	172.4	172.4	172.4	172.4	172.4	172.4	172.4	172.4	172.4	172.4
120°	190.8	191.1	191.2	191.0	190.7	190.4	190.1	189.8	190.1	190.4	190.7
122.5°	208.2	208.3	208.3	208.3	208.2	208.1	208.0	207.9	208.0	208.1	208.2
125°	225.6	225.7	225.7	225.7	225.7	225.7	225.7	225.7	225.7	225.7	225.7
127.5°	242.5	242.6	242.7	242.6	242.4	242.1	241.9	241.7	241.9	242.1	242.4
130°	259.8	259.8	259.8	259.7	259.4	259.2	258.9	258.7	258.9	259.2	259.4
132.5°	276.8	276.9	276.9	276.8	276.6	276.5	276.3	276.1	276.3	276.5	276.6
135°	293.2	293.2	293.2	293.0	292.5	292.0	291.6	291.1	291.6	292.0	292.5
137.5°	309.0	308.9	308.8	308.7	308.5	308.2	308.0	307.8	308.0	308.2	308.5
140°	325.2	325.2	325.2	325.1	325.0	324.8	324.7	324.5	324.7	324.8	325.0
142.5°	340.4	340.5	340.5	340.4	340.3	340.1	340.0	339.8	340.0	340.1	340.3
145°	355.1	355.0	355.0	354.8	354.5	354.2	353.9	353.6	353.9	354.2	354.5
147.5°	369.5	369.6	369.6	369.4	369.0	368.6	368.2	367.8	368.2	368.6	369.0
150°	382.1	382.1	382.1	381.9	381.6	381.3	380.9	380.6	380.9	381.3	381.6
152.5°	393.5	393.4	393.4	393.3	393.2	393.0	392.9	392.7	392.9	393.0	393.2
155°	405.1	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.2
157.5°	415.1	415.1	415.1	415.2	415.3	415.5	415.6	415.8	415.6	415.5	415.3
160°	424.6	424.7	424.7	424.7	424.8	424.9	425.0	425.1	425.0	424.9	424.8
162.5°	432.4	432.5	432.5	432.6	432.9	433.1	433.4	433.6	433.4	433.1	432.9
165°	439.8	439.9	440.0	440.1	440.3	440.6	440.8	441.0	440.8	440.6	440.3
167.5°	445.7	445.7	445.7	445.9	446.2	446.5	446.8	447.1	446.8	446.5	446.2
170°	450.4	450.3	450.3	450.5	450.9	451.3	451.7	452.1	451.7	451.3	450.9
172.5°	454.2	454.2	454.2	454.4	454.7	455.0	455.3	455.6	455.3	455.0	454.7
175°	456.9	457.0	457.0	457.2	457.6	458.0	458.4	458.8	458.4	458.0	457.6
177.5°	458.5	458.5	458.5	458.7	459.1	459.4	459.8	460.2	459.8	459.4	459.1
180°	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	921.4	918.3	919.8	912.1	905.1	895.0	886.5	885.0	883.4	888.1	885.0
5°	895.0	891.2	887.3	878.0	864.0	855.5	843.1	842.3	837.7	830.7	832.3
7.5°	866.4	864.0	858.6	843.9	831.5	816.8	806.7	798.2	794.3	788.1	785.8
10°	843.1	834.6	829.9	813.7	799.0	783.5	770.3	764.1	757.1	751.7	747.8
12.5°	811.4	809.0	795.9	782.7	770.3	752.5	742.4	724.6	715.3	719.9	718.4
15°	790.4	779.6	776.5	757.9	737.0	725.3	706.7	695.1	691.2	684.3	675.7
17.5°	762.5	755.6	744.7	727.7	703.6	687.4	674.2	663.3	658.7	649.4	642.4
20°	736.2	724.6	716.0	700.5	677.3	656.4	640.1	633.1	621.5	613.7	609.9
22.5°	712.2	703.6	691.2	668.0	647.8	627.7	608.3	598.2	587.4	582.7	576.5
25°	682.7	668.8	660.2	634.7	613.0	596.7	578.9	565.7	559.5	551.7	550.2
27.5°	654.0	640.9	630.8	608.3	582.0	561.0	550.2	540.9	530.1	530.1	526.2
30°	625.4	616.1	600.6	578.9	554.1	533.9	521.5	513.0	509.1	506.0	505.3
32.5°	596.7	584.3	575.0	545.5	527.0	508.4	499.1	492.1	487.4	486.7	487.4
35°	567.2	553.3	544.0	517.7	499.1	482.0	478.1	471.9	469.6	468.8	472.7
37.5°	536.3	525.4	513.8	492.1	471.2	461.1	453.3	451.0	450.2	454.9	456.4
40°	507.6	498.3	487.4	464.2	448.7	437.8	434.0	431.6	434.7	439.4	441.7
42.5°	480.5	467.3	458.8	437.8	423.9	417.7	413.0	413.0	416.1	421.6	425.4
45°	451.8	441.7	433.2	414.6	402.2	395.2	394.4	395.2	399.1	403.0	407.6
47.5°	423.9	413.8	404.5	389.0	378.2	374.3	373.5	374.3	380.5	385.9	391.3
50°	398.3	387.5	378.9	364.2	355.7	351.0	351.8	355.7	360.3	368.1	375.1
52.5°	368.1	360.3	352.6	339.4	331.7	328.6	330.9	334.0	342.5	347.9	356.5
55°	338.6	331.7	325.5	315.4	309.2	306.9	308.4	313.1	320.0	329.3	339.4
57.5°	311.5	303.8	297.6	290.6	283.6	284.4	285.2	291.4	299.9	308.4	320.0
60°	281.3	276.6	271.2	262.7	259.6	259.6	261.9	268.9	276.6	290.6	300.7
62.5°	254.2	248.0	244.1	238.7	234.0	234.8	240.2	246.4	255.7	267.4	280.5
65°	226.3	219.3	216.2	211.6	210.0	210.8	214.7	224.0	234.0	244.1	256.5
67.5°	195.3	193.0	189.9	185.2	186.8	187.5	191.4	199.2	210.0	220.1	234.0
70°	168.9	164.3	163.5	159.6	159.6	162.0	169.7	175.1	185.2	196.1	210.8
72.5°	141.0	137.2	137.2	134.1	136.4	138.7	142.6	150.3	159.6	170.5	182.9
75°	112.4	110.8	112.4	110.8	110.8	114.7	119.3	125.5	135.6	147.2	157.3
77.5°	86.8	86.8	86.0	88.3	88.3	90.7	96.9	103.1	110.8	120.1	131.0
80°	63.5	63.5	63.5	65.9	68.2	68.2	72.1	79.8	86.8	93.0	103.1
82.5°	43.4	43.4	43.4	44.9	48.0	48.0	52.7	57.3	65.1	70.5	75.2
85°	26.3	26.3	25.6	27.1	27.9	30.2	34.1	37.2	41.1	45.7	50.4
87.5°	11.6	11.6	12.4	13.2	13.9	15.5	17.0	18.6	22.5	24.0	26.3
90°	4.6	5.0	5.3	5.9	6.6	7.2	7.8	8.3	8.8	9.3	9.8
92.5°	13.4	13.9	14.1	14.5	14.8	15.2	15.6	15.8	16.1	16.3	16.6
95°	24.1	24.5	24.8	25.3	25.9	26.4	27.0	27.2	27.5	27.7	28.0
97.5°	36.7	37.0	37.3	37.9	38.6	39.2	39.8	40.1	40.4	40.7	41.0
100°	51.0	51.2	51.6	52.3	53.0	53.7	54.4	54.6	54.7	54.9	55.0
102.5°	66.5	66.5	66.8	67.4	68.1	68.7	69.3	69.5	69.8	70.0	70.3
105°	83.2	83.2	83.4	83.7	84.0	84.3	84.6	84.8	85.1	85.3	85.6
107.5°	100.6	100.6	100.6	100.7	100.8	100.8	100.9	101.2	101.6	101.9	102.2
110°	118.6	118.7	118.7	118.6	118.5	118.4	118.3	118.1	118.0	117.8	117.7

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	136.5	136.5	136.4	136.3	136.1	136.0	135.8	135.8	135.8	135.8	135.8
115°	155.0	155.0	154.9	154.7	154.6	154.4	154.2	154.1	154.1	154.0	153.9
117.5°	172.4	172.4	172.4	172.3	172.2	172.1	172.0	171.8	171.5	171.3	171.0
120°	191.0	191.2	191.1	190.8	190.6	190.3	190.1	189.7	189.3	189.0	188.6
122.5°	208.3	208.3	208.3	208.2	208.1	208.0	207.9	207.7	207.4	207.2	206.9
125°	225.7	225.7	225.7	225.6	225.5	225.4	225.3	225.1	225.0	224.8	224.7
127.5°	242.6	242.7	242.6	242.5	242.3	242.2	242.0	241.8	241.7	241.5	241.4
130°	259.7	259.8	259.8	259.8	259.8	259.8	259.8	259.6	259.5	259.3	259.2
132.5°	276.8	276.9	276.9	276.8	276.7	276.6	276.5	276.3	276.2	276.0	275.9
135°	293.0	293.2	293.2	293.2	293.2	293.2	293.2	293.0	292.9	292.7	292.6
137.5°	308.7	308.8	308.9	309.0	309.2	309.3	309.5	309.3	309.1	308.8	308.6
140°	325.1	325.2	325.2	325.2	325.2	325.2	325.2	325.1	325.0	324.9	324.8
142.5°	340.4	340.5	340.5	340.4	340.3	340.2	340.1	340.1	340.1	340.1	340.1
145°	354.8	355.0	355.0	355.1	355.2	355.3	355.4	355.3	355.2	355.1	355.0
147.5°	369.4	369.6	369.6	369.5	369.4	369.4	369.3	369.2	369.1	369.0	368.9
150°	381.9	382.1	382.1	382.1	382.1	382.1	382.1	382.1	382.1	382.1	382.1
152.5°	393.3	393.4	393.4	393.5	393.6	393.7	393.8	394.0	394.2	394.5	394.7
155°	405.2	405.2	405.2	405.1	405.0	404.9	404.8	405.1	405.4	405.7	406.0
157.5°	415.2	415.1	415.1	415.1	415.1	415.1	415.1	415.3	415.6	415.8	416.1
160°	424.7	424.7	424.7	424.6	424.5	424.4	424.3	424.5	424.8	425.0	425.3
162.5°	432.6	432.5	432.5	432.4	432.3	432.3	432.2	432.7	433.1	433.6	434.1
165°	440.1	440.0	439.9	439.8	439.6	439.5	439.3	439.8	440.2	440.7	441.2
167.5°	445.9	445.7	445.7	445.7	445.7	445.7	445.7	446.2	446.6	447.1	447.6
170°	450.5	450.3	450.3	450.4	450.5	450.5	450.6	451.1	451.6	452.1	452.6
172.5°	454.4	454.2	454.2	454.2	454.2	454.2	454.2	454.8	455.3	455.9	456.4
175°	457.2	457.0	457.0	456.9	456.8	456.8	456.7	457.3	457.8	458.4	458.9
177.5°	458.7	458.5	458.5	458.5	458.5	458.5	458.5	459.0	459.6	460.1	460.6
180°	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	882.6	881.9	878.0	879.5	874.9	876.4	878.8	879.5	882.6	880.3	879.5
5°	828.4	826.8	824.5	822.2	821.4	824.5	819.1	820.6	822.2	824.5	827.6
7.5°	784.2	783.5	781.1	777.3	775.7	774.2	774.9	780.4	779.6	778.8	784.2
10°	743.9	744.7	740.1	739.3	734.6	733.9	734.6	736.2	738.5	741.6	742.4
12.5°	702.1	712.2	703.6	700.5	693.6	697.4	699.0	692.0	695.9	698.2	709.8
15°	675.7	671.1	665.7	665.7	662.6	661.0	657.1	662.6	665.7	670.3	668.8
17.5°	639.3	631.6	628.5	625.4	626.1	629.2	620.7	633.1	633.1	635.4	631.6
20°	607.5	601.3	597.5	595.9	593.6	592.0	591.3	594.4	599.0	600.6	604.4
22.5°	574.2	574.2	568.0	565.7	564.1	561.8	565.7	563.4	566.5	569.6	575.8
25°	546.3	546.3	544.0	540.9	538.6	537.0	539.4	538.6	540.9	544.8	546.3
27.5°	523.9	521.5	520.8	520.0	519.2	520.0	519.2	521.5	523.9	524.6	523.1
30°	504.5	502.2	502.9	502.9	503.7	502.9	502.2	504.5	505.3	503.7	504.5
32.5°	486.7	486.7	488.2	489.0	489.0	489.8	490.5	489.0	489.8	487.4	488.2
35°	471.9	473.5	475.0	475.8	476.6	475.8	477.4	476.6	475.0	473.5	472.7
37.5°	457.2	458.8	461.9	462.6	465.0	465.7	464.2	464.2	463.4	460.3	458.8
40°	441.7	443.3	447.1	449.5	451.0	453.3	451.8	451.8	448.7	445.6	443.3
42.5°	427.0	430.1	434.0	436.3	439.4	439.4	439.4	437.8	434.0	430.9	428.5
45°	412.3	413.0	418.5	422.3	425.4	425.4	425.4	423.1	420.8	414.6	411.5
47.5°	396.0	398.3	404.5	408.4	411.5	412.3	412.3	409.9	405.3	399.9	396.0
50°	378.2	382.0	389.0	394.4	398.3	399.9	397.5	396.0	390.6	384.4	379.7
52.5°	361.1	365.8	374.3	378.9	384.4	385.1	384.4	382.0	375.8	367.3	363.4
55°	344.1	347.9	357.2	365.0	369.6	371.2	369.6	365.8	358.0	349.5	345.6
57.5°	325.5	330.9	341.0	348.7	354.1	354.9	353.4	349.5	343.3	332.4	327.0
60°	306.1	313.1	323.1	330.9	337.9	338.6	337.1	331.7	323.9	313.1	308.4
62.5°	286.7	292.1	303.8	312.3	317.7	321.6	318.5	313.1	305.3	294.5	287.5
65°	264.3	272.0	282.1	289.8	296.0	296.8	295.2	290.6	282.1	270.5	265.0
67.5°	242.6	248.0	258.1	268.1	270.5	272.8	270.5	265.8	258.8	248.8	241.0
70°	216.2	220.9	233.3	240.2	243.3	245.7	244.1	239.5	233.3	224.0	217.8
72.5°	189.9	193.7	205.4	210.8	217.0	216.2	215.4	212.3	203.8	197.6	193.7
75°	162.0	166.6	174.4	181.3	183.7	183.7	183.7	181.3	175.9	165.8	162.0
77.5°	136.4	138.7	144.9	148.8	151.1	151.9	151.1	147.2	144.1	137.2	134.8
80°	104.6	110.8	115.5	116.2	119.3	119.3	119.3	117.8	114.7	107.7	106.9
82.5°	79.0	80.6	85.2	87.6	89.1	88.3	88.3	85.2	84.5	80.6	79.0
85°	53.5	55.8	55.0	58.1	58.9	57.3	57.3	58.9	55.0	55.8	53.5
87.5°	29.4	29.4	31.0	30.2	33.3	33.3	31.8	32.5	31.0	30.2	29.4
90°	10.0	10.1	10.2	10.4	10.5	10.7	10.5	10.4	10.2	10.1	10.0
92.5°	16.7	16.7	16.8	16.9	17.0	17.1	17.0	16.9	16.8	16.7	16.7
95°	28.1	28.1	28.1	28.1	28.1	28.1	28.1	28.1	28.1	28.1	28.1
97.5°	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2
100°	55.1	55.1	55.1	55.1	55.1	55.1	55.1	55.1	55.1	55.1	55.1
102.5°	70.4	70.4	70.5	70.6	70.6	70.7	70.6	70.6	70.5	70.4	70.4
105°	85.7	85.8	86.0	86.3	86.5	86.7	86.5	86.3	86.0	85.8	85.7
107.5°	102.4	102.4	102.3	102.2	102.1	102.0	102.1	102.2	102.3	102.4	102.4
110°	117.6	117.7	118.0	118.2	118.5	118.7	118.5	118.2	118.0	117.7	117.6

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	135.8	135.8	135.8	135.8	135.8	135.8	135.8	135.8	135.8	135.8	135.8
115°	153.9	153.9	153.8	153.7	153.6	153.5	153.6	153.7	153.8	153.9	153.9
117.5°	170.9	170.8	170.6	170.3	170.1	169.9	170.1	170.3	170.6	170.8	170.9
120°	188.4	188.5	188.6	188.8	188.9	189.1	188.9	188.8	188.6	188.5	188.4
122.5°	206.8	206.6	206.2	205.9	205.5	205.1	205.5	205.9	206.2	206.6	206.8
125°	224.6	224.5	224.4	224.2	224.1	223.9	224.1	224.2	224.4	224.5	224.6
127.5°	241.3	241.3	241.2	241.1	241.1	241.0	241.1	241.1	241.2	241.3	241.3
130°	259.1	258.9	258.6	258.3	258.0	257.7	258.0	258.3	258.6	258.9	259.1
132.5°	275.8	275.8	275.7	275.6	275.5	275.4	275.5	275.6	275.7	275.8	275.8
135°	292.5	292.4	292.1	291.9	291.6	291.4	291.6	291.9	292.1	292.4	292.5
137.5°	308.5	308.5	308.6	308.7	308.7	308.8	308.7	308.7	308.6	308.5	308.5
140°	324.8	324.8	324.7	324.6	324.6	324.5	324.6	324.6	324.7	324.8	324.8
142.5°	340.1	340.1	340.1	340.1	340.1	340.1	340.1	340.1	340.1	340.1	340.1
145°	355.0	354.9	354.7	354.4	354.2	354.0	354.2	354.4	354.7	354.9	355.0
147.5°	368.9	368.9	368.8	368.7	368.6	368.5	368.6	368.7	368.8	368.9	368.9
150°	382.1	382.1	382.0	381.9	381.8	381.7	381.8	381.9	382.0	382.1	382.1
152.5°	394.8	394.7	394.5	394.2	394.0	393.8	394.0	394.2	394.5	394.7	394.8
155°	406.2	406.0	405.7	405.4	405.1	404.8	405.1	405.4	405.7	406.0	406.2
157.5°	416.2	416.1	415.8	415.6	415.3	415.1	415.3	415.6	415.8	416.1	416.2
160°	425.4	425.2	424.8	424.4	424.0	423.6	424.0	424.4	424.8	425.2	425.4
162.5°	434.3	434.1	433.7	433.3	432.9	432.5	432.9	433.3	433.7	434.1	434.3
165°	441.4	441.2	440.9	440.6	440.3	440.0	440.3	440.6	440.9	441.2	441.4
167.5°	447.8	447.6	447.1	446.6	446.2	445.7	446.2	446.6	447.1	447.6	447.8
170°	452.8	452.5	452.0	451.4	450.9	450.3	450.9	451.4	452.0	452.5	452.8
172.5°	456.7	456.4	455.9	455.3	454.8	454.2	454.8	455.3	455.9	456.4	456.7
175°	459.2	458.9	458.4	457.8	457.3	456.7	457.3	457.8	458.4	458.9	459.2
177.5°	460.9	460.6	460.0	459.3	458.7	458.1	458.7	459.3	460.0	460.6	460.9
180°	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	879.5	884.2	879.5	882.6	884.2	888.1	889.6	896.6	898.9	904.3	904.3
5°	826.8	829.2	829.9	833.0	836.1	843.9	849.3	859.4	871.0	872.6	879.5
7.5°	784.2	788.1	794.3	792.0	797.4	809.0	816.0	828.4	840.0	846.2	854.7
10°	746.3	750.9	753.2	755.6	765.6	775.7	786.6	795.1	810.6	819.9	826.8
12.5°	715.3	711.4	716.0	724.6	736.2	742.4	757.1	770.3	781.9	792.0	798.2
15°	675.0	678.1	682.7	697.4	700.5	716.0	721.5	736.2	757.9	767.2	774.9
17.5°	636.2	646.3	655.6	661.0	670.3	682.7	698.2	714.5	728.4	739.3	748.6
20°	605.2	615.3	620.7	624.6	633.9	650.9	665.7	685.8	703.6	712.2	724.6
22.5°	580.4	580.4	588.2	599.8	605.2	621.5	633.9	655.6	675.0	685.8	697.4
25°	549.4	554.1	560.3	570.3	578.1	591.3	609.1	627.7	648.6	657.9	672.6
27.5°	523.9	529.3	537.8	540.1	547.9	559.5	578.1	598.2	619.9	630.0	642.4
30°	504.5	507.6	510.7	515.3	522.3	532.4	547.9	565.7	592.0	599.8	615.3
32.5°	487.4	489.0	490.5	494.4	498.3	508.4	520.8	540.1	561.8	573.4	587.4
35°	471.9	470.4	471.2	473.5	477.4	481.2	494.4	510.7	530.8	544.8	555.6
37.5°	457.2	454.1	453.3	453.3	454.9	459.5	469.6	483.6	505.3	516.9	527.7
40°	440.9	437.8	436.3	435.5	434.7	437.8	445.6	459.5	476.6	487.4	499.8
42.5°	425.4	422.3	418.5	417.7	416.1	417.7	423.1	436.3	451.0	461.9	471.9
45°	409.9	404.5	399.9	396.8	397.5	395.2	399.1	409.2	426.2	433.2	443.3
47.5°	392.9	386.7	380.5	377.4	374.3	375.8	377.4	385.9	400.6	407.6	417.7
50°	376.6	368.1	361.1	357.2	354.9	353.4	354.9	363.4	374.3	380.5	389.0
52.5°	358.0	349.5	342.5	336.3	333.2	330.9	331.7	339.4	349.5	355.7	364.2
55°	341.0	330.1	320.8	313.1	310.7	310.0	309.2	314.6	323.1	329.3	336.3
57.5°	321.6	310.7	300.7	291.4	286.7	285.9	285.9	287.5	298.3	303.0	306.9
60°	302.2	290.6	279.7	271.2	264.3	261.9	261.2	264.3	269.7	274.3	279.7
62.5°	280.5	268.9	255.7	248.0	241.0	234.8	237.1	237.9	245.7	248.0	252.6
65°	259.6	246.4	235.6	223.2	215.4	211.6	210.0	211.6	217.8	218.5	221.6
67.5°	235.6	223.2	210.0	201.5	194.5	187.5	186.0	186.0	189.1	191.4	195.3
70°	212.3	199.9	185.2	175.9	168.9	162.7	160.4	159.6	162.0	163.5	167.4
72.5°	185.2	172.8	162.0	151.9	143.4	138.7	136.4	134.8	137.2	138.7	139.5
75°	156.5	146.5	135.6	125.5	120.1	115.5	112.4	110.0	111.6	111.6	111.6
77.5°	129.4	119.3	110.8	103.8	96.9	91.4	89.1	86.8	87.6	87.6	89.1
80°	100.7	93.8	86.8	80.6	74.4	69.7	68.2	65.9	64.3	63.5	63.5
82.5°	74.4	69.0	62.8	57.3	54.2	49.6	48.0	44.9	44.9	44.2	44.2
85°	49.6	46.5	40.3	36.4	34.1	31.8	30.2	28.7	26.3	26.3	25.6
87.5°	26.3	24.8	23.2	18.6	18.6	16.3	15.5	14.7	12.4	13.2	13.2
90°	9.8	9.3	8.8	8.3	7.8	7.2	6.6	5.9	5.3	5.0	4.6
92.5°	16.6	16.3	16.1	15.8	15.6	15.2	14.8	14.5	14.1	13.9	13.4
95°	28.0	27.7	27.5	27.2	27.0	26.4	25.9	25.3	24.8	24.5	24.1
97.5°	41.0	40.7	40.4	40.1	39.8	39.2	38.6	37.9	37.3	37.0	36.7
100°	55.0	54.9	54.7	54.6	54.4	53.7	53.0	52.3	51.6	51.2	51.0
102.5°	70.3	70.0	69.8	69.5	69.3	68.7	68.1	67.4	66.8	66.5	66.5
105°	85.6	85.3	85.1	84.8	84.6	84.3	84.0	83.7	83.4	83.2	83.2
107.5°	102.2	101.9	101.6	101.2	100.9	100.8	100.8	100.7	100.6	100.6	100.6
110°	117.7	117.8	118.0	118.1	118.3	118.4	118.5	118.6	118.7	118.7	118.6

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	135.8	135.8	135.8	135.8	135.8	136.0	136.1	136.3	136.4	136.5	136.5
115°	153.9	154.0	154.1	154.1	154.2	154.4	154.6	154.7	154.9	155.0	155.0
117.5°	171.0	171.3	171.5	171.8	172.0	172.1	172.2	172.3	172.4	172.4	172.4
120°	188.6	189.0	189.3	189.7	190.1	190.3	190.6	190.8	191.1	191.2	191.0
122.5°	206.9	207.2	207.4	207.7	207.9	208.0	208.1	208.2	208.3	208.3	208.3
125°	224.7	224.8	225.0	225.1	225.3	225.4	225.5	225.6	225.7	225.7	225.7
127.5°	241.4	241.5	241.7	241.8	242.0	242.2	242.3	242.5	242.6	242.7	242.6
130°	259.2	259.3	259.5	259.6	259.8	259.8	259.8	259.8	259.8	259.8	259.7
132.5°	275.9	276.0	276.2	276.3	276.5	276.6	276.7	276.8	276.9	276.9	276.8
135°	292.6	292.7	292.9	293.0	293.2	293.2	293.2	293.2	293.2	293.2	293.0
137.5°	308.6	308.8	309.1	309.3	309.5	309.3	309.2	309.0	308.9	308.8	308.7
140°	324.8	324.9	325.0	325.1	325.2	325.2	325.2	325.2	325.2	325.2	325.1
142.5°	340.1	340.1	340.1	340.1	340.1	340.2	340.3	340.4	340.5	340.5	340.4
145°	355.0	355.1	355.2	355.3	355.4	355.3	355.2	355.1	355.0	355.0	354.8
147.5°	368.9	369.0	369.1	369.2	369.3	369.4	369.4	369.5	369.6	369.6	369.4
150°	382.1	382.1	382.1	382.1	382.1	382.1	382.1	382.1	382.1	382.1	381.9
152.5°	394.7	394.5	394.2	394.0	393.8	393.7	393.6	393.5	393.4	393.4	393.3
155°	406.0	405.7	405.4	405.1	404.8	404.9	405.0	405.1	405.2	405.2	405.2
157.5°	416.1	415.8	415.6	415.3	415.1	415.1	415.1	415.1	415.1	415.1	415.2
160°	425.3	425.0	424.8	424.5	424.3	424.4	424.5	424.6	424.7	424.7	424.7
162.5°	434.1	433.6	433.1	432.7	432.2	432.3	432.3	432.4	432.5	432.5	432.6
165°	441.2	440.7	440.2	439.8	439.3	439.5	439.6	439.8	439.9	440.0	440.1
167.5°	447.6	447.1	446.6	446.2	445.7	445.7	445.7	445.7	445.7	445.7	445.9
170°	452.6	452.1	451.6	451.1	450.6	450.5	450.5	450.4	450.3	450.3	450.5
172.5°	456.4	455.9	455.3	454.8	454.2	454.2	454.2	454.2	454.2	454.2	454.4
175°	458.9	458.4	457.8	457.3	456.7	456.8	456.8	456.9	457.0	457.0	457.2
177.5°	460.6	460.1	459.6	459.0	458.5	458.5	458.5	458.5	458.5	458.5	458.7
180°	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5	459.5

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	935.3	935.3	935.3	935.3
2.5°	909.8	917.5	924.5	935.3
5°	889.6	900.5	915.2	931.5
7.5°	866.4	883.4	902.8	925.3
10°	844.7	864.0	888.8	916.0
12.5°	822.2	845.4	872.6	902.0
15°	796.6	819.9	850.1	889.6
17.5°	773.4	801.3	833.8	875.7
20°	746.3	772.6	808.3	856.3
22.5°	722.2	752.5	792.0	833.8
25°	695.9	722.2	761.8	812.1
27.5°	669.5	702.1	740.1	788.9
30°	644.0	671.1	712.2	763.3
32.5°	616.1	648.6	686.6	734.6
35°	585.8	616.8	652.5	704.4
37.5°	558.7	588.9	625.4	671.1
40°	528.5	560.3	593.6	639.3
42.5°	499.1	527.7	561.0	602.9
45°	470.4	495.2	525.4	561.8
47.5°	440.9	461.9	489.8	522.3
50°	409.2	431.6	452.6	479.7
52.5°	379.7	399.1	416.1	438.6
55°	351.0	364.2	378.2	395.2
57.5°	320.8	330.9	341.0	358.8
60°	290.6	299.9	305.3	316.9
62.5°	261.2	265.0	272.0	279.0
65°	228.6	234.0	237.9	246.4
67.5°	199.2	201.5	205.4	210.8
70°	168.2	173.6	175.1	179.0
72.5°	141.8	144.1	145.7	146.5
75°	112.4	114.7	116.2	120.9
77.5°	88.3	87.6	90.7	91.4
80°	65.1	62.8	63.5	66.6
82.5°	42.6	43.4	42.6	42.6
85°	26.3	25.6	24.0	24.8
87.5°	11.6	11.6	10.8	10.8
90°	3.7	2.8	2.0	1.1
92.5°	12.3	11.3	10.2	9.2
95°	23.4	22.7	22.0	21.3
97.5°	36.0	35.4	34.7	34.1
100°	50.7	50.4	50.1	49.8
102.5°	66.4	66.3	66.2	66.1
105°	83.1	83.0	82.9	82.8
107.5°	100.5	100.4	100.3	100.2
110°	118.5	118.3	118.2	118.0

TEST NUMBER: P1025579

CATALOG NUMBER: S124DIP-B575D365UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	136.5	136.5	136.5	136.5
115°	155.0	155.0	155.0	155.0
117.5°	172.4	172.4	172.4	172.4
120°	190.7	190.4	190.1	189.8
122.5°	208.2	208.1	208.0	207.9
125°	225.7	225.7	225.7	225.7
127.5°	242.4	242.1	241.9	241.7
130°	259.4	259.2	258.9	258.7
132.5°	276.6	276.5	276.3	276.1
135°	292.5	292.0	291.6	291.1
137.5°	308.5	308.2	308.0	307.8
140°	325.0	324.8	324.7	324.5
142.5°	340.3	340.1	340.0	339.8
145°	354.5	354.2	353.9	353.6
147.5°	369.0	368.6	368.2	367.8
150°	381.6	381.3	380.9	380.6
152.5°	393.2	393.0	392.9	392.7
155°	405.2	405.2	405.2	405.2
157.5°	415.3	415.5	415.6	415.8
160°	424.8	424.9	425.0	425.1
162.5°	432.9	433.1	433.4	433.6
165°	440.3	440.6	440.8	441.0
167.5°	446.2	446.5	446.8	447.1
170°	450.9	451.3	451.7	452.1
172.5°	454.7	455.0	455.3	455.6
175°	457.6	458.0	458.4	458.8
177.5°	459.1	459.4	459.8	460.2
180°	459.5	459.5	459.5	459.5

(END OF REPORT)