

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025607

Luminaire Tested: S124DIP-B575D365UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025607
REPORT IS A COMBINATION OF REPORTS P996192 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D365UB50-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3750.0 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	97	93	90	96	92	88	85	82	79	77	72	70	68	63	62	61
2	93	85	79	74	87	81	75	71	72	68	64	64	60	58	56	54	51
3	85	75	68	62	80	71	65	59	64	58	54	57	52	49	50	47	44
4	78	67	59	53	73	63	56	51	57	51	46	51	46	42	45	41	38
5	72	60	52	46	67	57	49	44	51	45	40	46	41	37	41	37	34
6	66	54	46	40	62	51	44	38	46	40	35	41	36	33	37	33	30
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	27
8	57	45	37	31	54	42	35	30	38	32	28	35	30	26	31	27	24
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22
10	50	38	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7335	7335	7335	7335
5°	7316	8414	7359	6323
10°	7261	9817	7316	5547
15°	7174	11317	7225	4964
20°	7082	12272	7132	4450
25°	6946	12131	7012	4071
30°	6813	10027	6897	3876
35°	6627	7472	6700	3758
40°	6410	5629	6473	3699
45°	6079	4518	6154	3621
50°	5683	3806	5765	3584
55°	5218	3313	5299	3542
60°	4765	2917	4904	3483
65°	4340	2510	4381	3338
70°	3840	2065	3924	3073
75°	3352	1586	3328	2611
80°	2636	1043	2603	1983
85°	1732	470	1630	1155

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 9484 cd/sqm

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.5	2.3
10°-20°	270.2	7.2
20°-30°	429.2	11.4
30°-40°	477.0	12.7
40°-50°	433.7	11.6
50°-60°	354.5	9.5
60°-70°	253.0	6.7
70°-80°	139.2	3.7
80°-90°	38.3	1.0
90°-100°	126.1	3.4
100°-110°	263.3	7.0
110°-120°	234.0	6.2
120°-130°	197.0	5.3
130°-140°	164.4	4.4
140°-150°	125.5	3.3
150°-160°	88.2	2.4
160°-170°	51.9	1.4
170°-180°	16.9	0.5
0°-30°	787.0	21.0
0°-40°	1263.9	33.7
0°-60°	2052.1	54.7
0°-90°	2482.7	66.2
90°-120°	623.4	16.6
90°-150°	1110.3	29.6
90°-180°	1267.0	33.8
0°-180°	3750.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	900	900	900	900	900	
5°	896	1055	901	793	896	85
15°	856	1449	862	636	856	241
25°	781	1539	788	516	781	360
35°	677	910	685	458	677	423
45°	540	510	547	409	540	417
55°	380	334	386	357	380	342
65°	237	215	239	285	237	234
75°	116	107	116	177	116	122
85°	24	22	22	55	24	28
90°	0	7	0	7	0	2
95°	11	83	11	83	11	12
105°	40	481	40	481	40	43
115°	70	462	70	462	70	70
125°	98	368	98	368	98	87
135°	117	330	117	330	117	90
145°	134	269	134	269	134	84
155°	153	225	153	225	153	70
165°	166	197	166	197	166	47
175°	174	177	174	177	174	16
180°	174	174	174	174	174	

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5
2.5°	899.5	908.4	912.1	915.1	924.8	927.8	928.5	933.0	936.7	937.5	937.5
5°	895.7	909.9	921.1	931.5	947.2	953.9	962.1	971.0	982.9	990.4	994.1
7.5°	889.8	910.6	927.8	945.7	967.3	980.7	988.1	1012.0	1028.4	1041.8	1058.2
10°	880.8	907.7	932.3	958.3	988.9	1005.3	1021.7	1050.7	1073.8	1099.9	1120.8
12.5°	867.4	902.4	932.3	968.8	1006.8	1026.1	1045.5	1096.2	1123.0	1146.1	1183.4
15°	855.5	890.5	933.0	970.3	1017.2	1046.3	1074.6	1107.4	1149.9	1199.8	1235.5
17.5°	842.1	886.0	925.5	977.7	1029.9	1057.4	1080.5	1131.2	1190.8	1240.0	1272.8
20°	823.5	868.2	920.3	975.5	1037.3	1058.9	1089.5	1157.3	1211.0	1259.4	1313.1
22.5°	801.8	854.0	909.1	962.1	1026.1	1071.6	1105.1	1164.8	1229.6	1285.5	1345.8
25°	781.0	837.6	886.0	958.3	1026.1	1056.7	1094.7	1165.5	1236.3	1304.1	1366.0
27.5°	758.6	811.5	877.1	934.5	1011.2	1044.8	1085.8	1163.3	1238.5	1306.3	1372.7
30°	734.0	790.7	845.1	912.9	987.4	1030.6	1068.6	1152.8	1229.6	1300.4	1362.2
32.5°	706.5	760.1	818.2	882.3	960.6	1004.5	1052.2	1138.7	1220.6	1281.8	1329.4
35°	677.4	731.8	782.5	848.0	928.5	972.5	1018.7	1114.1	1195.3	1245.2	1272.8
37.5°	645.3	696.8	746.7	811.5	892.0	939.0	985.9	1078.3	1155.1	1196.8	1189.3
40°	614.8	661.0	707.2	768.3	852.5	902.4	943.4	1036.6	1103.6	1121.5	1096.9
42.5°	579.8	619.3	664.0	726.6	808.5	855.5	906.9	991.9	1041.8	1034.3	992.6
45°	540.3	575.3	620.0	678.9	762.3	810.8	854.0	934.5	971.0	952.4	876.4
47.5°	502.3	536.5	573.1	631.9	713.2	754.1	798.1	870.4	891.3	851.8	775.8
50°	461.3	489.6	527.6	583.5	659.5	702.7	739.2	797.4	804.8	756.4	677.4
52.5°	421.8	445.6	482.1	537.3	608.1	642.4	678.1	729.6	723.6	673.7	597.7
55°	380.1	402.4	435.9	486.6	549.2	582.0	612.6	658.0	645.3	593.9	527.6
57.5°	345.0	360.7	393.5	440.4	491.8	527.6	553.7	589.5	570.1	518.7	456.8
60°	304.8	324.2	351.7	389.7	440.4	464.3	487.4	511.2	497.8	448.6	393.5
62.5°	268.3	283.2	307.0	343.5	383.0	404.6	429.2	444.1	430.7	385.3	339.1
65°	237.0	248.9	267.5	297.3	335.3	353.2	367.4	381.5	370.4	327.9	294.4
67.5°	202.7	213.1	228.8	252.6	284.7	297.3	310.8	320.4	307.8	279.5	246.7
70°	172.1	179.6	194.5	212.4	234.7	246.7	257.8	267.5	256.4	232.5	207.9
72.5°	140.8	146.8	160.2	172.9	193.0	201.2	209.4	216.9	213.1	190.8	170.7
75°	116.3	118.5	127.4	137.9	150.5	159.5	165.4	169.9	166.9	149.0	136.4
77.5°	87.9	90.9	97.6	105.8	117.0	122.2	125.9	130.4	126.7	112.5	103.6
80°	64.1	64.8	68.6	76.0	83.5	84.2	87.9	93.9	91.7	82.0	75.3
82.5°	41.0	43.2	44.7	49.2	54.4	55.9	58.1	59.6	58.9	52.9	50.7
85°	23.8	23.8	25.3	28.3	29.8	32.0	32.8	33.5	35.0	31.3	29.1
87.5°	10.4	11.2	11.2	11.9	13.4	13.4	14.2	14.9	15.6	14.9	12.7
90°	0.3	1.0	2.1	2.4	2.7	2.7	2.7	4.8	4.8	5.5	6.2
92.5°	4.8	6.8	10.6	15.7	21.9	26.4	30.8	52.0	85.1	117.3	134.0
95°	11.3	12.3	15.7	20.2	28.4	35.6	42.7	72.5	128.5	210.2	278.6
97.5°	18.8	18.8	21.9	26.0	33.2	39.4	45.5	69.1	117.3	201.4	298.1
100°	26.0	26.0	28.4	32.5	39.0	44.4	49.9	70.1	108.7	178.4	274.9
102.5°	32.8	33.5	35.6	39.3	45.5	50.6	55.7	73.5	106.3	163.1	245.8
105°	40.0	41.0	42.7	46.8	53.0	58.0	62.9	79.3	107.7	155.5	224.3
107.5°	47.9	48.5	50.3	54.7	60.5	65.4	70.4	85.5	111.8	153.5	210.2
110°	55.7	56.4	58.1	62.2	68.4	73.0	77.6	92.6	116.6	154.2	203.7

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	63.2	63.9	66.0	69.7	75.9	80.5	85.1	99.5	121.7	156.2	200.7
115°	70.4	71.4	73.8	77.3	83.8	88.4	93.0	106.7	127.2	159.0	200.0
117.5°	77.9	79.0	81.0	84.8	90.9	95.7	100.5	113.5	132.6	161.7	199.6
120°	85.5	86.1	88.5	92.3	98.1	102.9	107.7	120.7	138.5	164.8	199.6
122.5°	92.3	93.0	95.4	98.8	105.3	109.9	114.5	127.5	143.9	167.9	199.3
125°	98.1	99.5	101.5	105.3	111.8	116.6	121.4	133.7	149.4	170.9	199.0
127.5°	103.6	104.6	107.0	111.1	117.9	122.7	127.5	139.5	154.2	173.3	198.3
130°	108.0	109.4	112.1	117.3	123.8	128.8	133.7	145.3	158.6	176.1	197.9
132.5°	112.5	113.5	117.3	122.0	129.2	133.8	138.5	150.1	163.1	178.4	197.6
135°	116.6	117.9	121.4	127.2	134.3	138.8	143.2	154.5	166.8	180.8	197.3
137.5°	120.7	122.0	125.8	131.3	138.8	143.0	147.3	157.9	169.6	182.2	197.3
140°	125.1	126.1	129.9	135.7	142.9	147.0	151.1	161.4	172.3	183.9	196.9
142.5°	129.9	130.9	134.3	139.8	146.7	150.6	154.5	164.4	174.3	185.3	196.9
145°	134.3	135.4	138.8	143.6	150.1	153.8	157.6	166.5	175.7	185.6	196.2
147.5°	139.5	139.8	142.9	148.0	153.5	156.9	160.3	168.9	177.1	186.0	195.2
150°	144.3	144.6	147.3	151.4	156.6	159.8	163.1	170.6	178.1	186.0	194.2
152.5°	148.7	148.7	151.4	155.2	159.6	162.6	165.5	172.0	178.8	185.3	192.5
155°	152.8	153.2	155.2	158.6	162.4	165.0	167.5	173.3	179.1	184.6	190.8
157.5°	156.9	156.9	159.0	161.7	165.1	167.1	169.2	174.3	179.1	183.9	189.0
160°	160.7	160.7	162.0	164.4	167.2	169.0	170.9	175.0	179.1	182.9	187.0
162.5°	164.1	163.7	164.8	166.8	169.2	170.6	172.0	175.7	179.1	181.9	184.9
165°	166.5	166.5	167.2	168.9	170.6	171.6	172.6	175.7	178.4	180.5	182.9
167.5°	169.2	168.9	169.2	170.6	171.6	172.4	173.3	175.7	177.8	179.1	180.8
170°	170.9	170.6	170.9	172.0	172.6	173.1	173.7	175.4	177.1	177.8	178.8
172.5°	172.6	172.3	172.3	173.0	173.3	173.6	174.0	175.0	176.4	176.4	176.7
175°	173.7	173.3	173.3	173.7	174.0	174.0	174.0	174.7	175.7	175.4	175.4
177.5°	174.3	174.0	173.7	174.0	174.0	174.0	174.0	174.3	175.0	174.3	174.3
180°	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5
2.5°	939.7	953.1	959.1	960.6	968.8	963.5	965.8	965.0	971.0	971.7	971.7
5°	1008.3	1023.9	1029.1	1036.6	1047.8	1050.7	1048.5	1053.0	1061.2	1055.2	1064.2
7.5°	1080.5	1097.7	1109.6	1126.0	1129.7	1139.4	1145.4	1150.6	1152.1	1152.8	1154.3
10°	1147.6	1169.2	1185.6	1213.2	1219.2	1224.4	1250.5	1240.0	1253.4	1249.0	1250.5
12.5°	1202.0	1244.5	1257.9	1304.1	1308.6	1326.5	1325.0	1341.4	1344.3	1350.3	1344.3
15°	1273.6	1322.7	1344.3	1370.4	1385.3	1406.2	1409.9	1432.3	1441.2	1449.4	1441.2
17.5°	1339.1	1365.2	1420.4	1441.2	1450.9	1462.1	1490.4	1498.6	1512.0	1506.8	1521.7
20°	1371.9	1409.2	1467.3	1503.1	1518.0	1528.4	1552.3	1564.9	1570.1	1570.1	1571.6
22.5°	1401.0	1454.6	1497.9	1538.8	1552.3	1559.7	1573.9	1583.6	1585.8	1587.3	1588.8
25°	1427.1	1475.5	1510.5	1533.6	1538.8	1538.8	1547.0	1541.1	1531.4	1538.8	1543.3
27.5°	1427.1	1461.3	1477.0	1485.2	1485.2	1465.1	1453.1	1428.6	1407.7	1401.7	1415.1
30°	1403.2	1418.9	1397.3	1377.1	1361.5	1348.1	1301.1	1263.9	1256.4	1251.2	1271.3
32.5°	1348.1	1328.0	1285.5	1227.4	1204.3	1173.7	1137.2	1108.9	1091.7	1085.8	1081.3
35°	1250.5	1198.3	1143.1	1064.9	1048.5	1009.8	959.8	939.0	910.6	909.9	919.6
37.5°	1143.9	1063.4	1003.8	929.3	906.2	865.2	818.2	796.6	777.2	762.3	780.2
40°	1019.4	949.4	858.5	797.4	764.6	743.0	703.5	679.6	670.7	663.2	674.4
42.5°	903.2	826.4	755.6	693.0	666.2	641.6	615.5	592.4	585.7	585.0	593.2
45°	787.7	712.4	646.8	593.2	576.0	561.1	535.8	529.1	517.9	510.5	514.2
47.5°	695.3	617.8	563.4	522.4	507.5	494.8	478.4	467.2	457.6	454.6	459.0
50°	604.4	552.2	496.3	462.0	450.8	438.9	426.3	415.8	411.4	408.4	411.4
52.5°	531.3	475.4	437.4	409.9	398.7	389.7	380.8	376.3	370.4	371.9	374.8
55°	465.8	416.6	384.5	364.4	357.7	354.0	342.8	337.6	335.3	333.9	335.3
57.5°	403.9	368.1	344.3	327.1	318.2	316.0	307.0	307.0	304.8	302.6	303.3
60°	354.7	324.2	301.1	287.6	286.2	282.4	276.5	275.7	270.5	272.7	273.5
62.5°	304.8	280.2	264.5	256.4	251.1	249.6	245.9	245.2	242.9	243.7	242.2
65°	265.3	245.2	229.5	222.8	220.6	219.8	216.9	214.6	213.1	214.6	213.1
67.5°	225.8	212.4	200.5	193.8	190.8	190.0	187.8	186.3	187.0	184.8	186.3
70°	188.5	175.1	167.7	163.9	162.5	160.2	160.2	160.2	160.2	158.7	158.0
72.5°	158.7	145.3	140.1	137.9	136.4	135.6	133.4	134.1	133.4	132.6	135.6
75°	125.9	117.7	112.5	110.3	111.8	109.5	107.3	108.8	106.6	107.3	110.3
77.5°	95.4	91.7	88.7	87.2	85.7	84.2	84.2	82.7	82.7	82.7	82.7
80°	69.3	68.6	63.3	62.6	62.6	61.1	61.1	61.1	61.1	60.4	61.1
82.5°	46.2	45.5	44.0	43.2	41.7	42.5	42.5	41.0	41.0	40.2	41.0
85°	26.8	26.8	25.3	24.6	23.8	24.6	23.1	22.4	23.1	22.4	23.1
87.5°	12.7	11.2	11.9	11.2	9.7	10.4	8.9	9.7	8.9	8.2	9.7
90°	5.8	6.2	6.5	6.8	6.8	6.8	7.2	7.5	7.2	7.2	7.2
92.5°	111.4	82.4	61.5	48.5	44.2	40.0	34.9	32.5	31.1	31.1	31.1
95°	286.5	253.3	200.3	154.5	138.0	121.4	104.6	94.0	87.9	83.4	87.9
97.5°	359.3	364.8	338.4	300.8	281.6	262.5	239.3	218.8	208.5	200.3	208.5
100°	362.4	412.3	419.1	402.4	389.8	377.1	347.3	326.5	316.2	313.5	316.2
102.5°	336.7	409.9	450.6	460.8	457.4	454.0	438.6	424.9	414.0	411.9	414.0
105°	304.6	382.9	442.0	475.9	482.9	489.9	490.6	487.8	483.0	481.0	483.0
107.5°	278.3	349.7	413.6	460.8	475.2	489.5	504.6	510.7	513.5	513.8	513.5
110°	259.5	320.3	379.5	429.0	447.8	466.6	490.9	505.3	511.4	514.5	511.4

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	248.9	298.8	349.4	395.5	414.3	433.1	461.5	479.6	488.9	494.3	488.9
115°	243.1	285.8	327.8	367.8	384.2	400.7	427.7	448.2	459.1	461.8	459.1
117.5°	240.0	278.3	313.8	346.3	360.6	375.0	398.9	416.7	428.3	430.1	428.3
120°	237.6	273.5	305.3	332.6	344.8	356.9	376.4	391.4	400.3	404.1	400.3
122.5°	234.9	269.4	299.8	324.1	334.4	344.6	360.3	372.6	379.8	383.6	379.8
125°	231.8	264.6	294.0	317.6	327.0	336.4	350.1	360.0	366.5	368.5	366.5
127.5°	227.7	259.1	287.5	311.1	320.0	328.9	342.5	351.4	356.9	358.9	356.9
130°	223.9	252.3	279.3	302.5	311.6	320.7	334.7	343.2	348.7	350.7	348.7
132.5°	220.5	245.1	270.1	292.6	301.6	310.7	324.4	334.3	339.5	341.5	339.5
135°	217.1	238.6	260.8	281.7	290.2	298.8	312.5	322.0	327.5	329.5	327.5
137.5°	214.0	232.5	251.9	270.1	278.0	285.8	298.8	308.7	313.1	315.5	313.1
140°	211.6	227.3	243.4	258.8	266.0	273.1	285.1	292.6	297.4	300.1	297.4
142.5°	209.6	222.5	236.2	248.9	254.8	260.8	271.1	277.9	282.0	283.7	282.0
145°	207.2	218.1	229.7	240.0	244.8	249.6	258.1	263.9	267.3	269.0	267.3
147.5°	205.1	214.3	223.9	232.5	236.4	240.3	246.8	251.9	254.7	255.4	254.7
150°	202.7	210.9	218.8	225.6	228.7	231.8	237.2	241.7	243.7	244.1	243.7
152.5°	200.0	207.2	213.7	219.8	222.2	224.6	229.0	232.5	233.5	233.8	233.5
155°	197.3	203.4	208.9	214.0	216.0	218.1	221.5	224.3	225.3	225.3	225.3
157.5°	194.5	199.3	204.1	208.5	210.2	211.9	214.7	216.7	217.4	217.4	217.4
160°	191.4	195.5	199.3	203.1	204.4	205.8	207.8	209.9	210.2	210.2	210.2
162.5°	188.7	191.8	194.9	197.6	198.8	200.0	201.4	203.4	203.7	203.4	203.7
165°	185.6	188.4	190.4	192.8	193.6	194.5	195.9	197.3	196.9	196.6	196.9
167.5°	182.9	184.9	186.7	188.7	189.2	189.7	190.4	191.4	191.4	191.1	191.4
170°	180.2	181.9	182.9	184.3	184.8	185.3	186.0	186.3	186.0	186.0	186.0
172.5°	177.8	179.1	179.8	180.5	180.8	181.2	181.5	181.9	181.5	180.8	181.5
175°	176.1	176.7	177.1	177.8	177.8	177.8	177.8	178.4	177.8	177.1	177.8
177.5°	174.7	175.0	175.4	175.4	175.6	175.7	175.4	175.7	175.0	174.3	175.0
180°	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5
2.5°	970.3	968.0	965.0	965.0	961.3	961.3	955.4	944.9	936.0	933.0	934.5
5°	1053.0	1053.7	1049.2	1045.5	1038.8	1033.6	1023.9	1005.3	999.3	987.4	979.2
7.5°	1147.6	1144.6	1136.4	1130.5	1129.0	1117.1	1096.2	1073.8	1056.0	1044.0	1026.9
10°	1254.2	1242.3	1230.3	1226.6	1217.7	1197.5	1173.7	1149.1	1124.5	1098.4	1069.4
12.5°	1343.6	1320.5	1319.8	1310.8	1293.7	1282.5	1254.2	1219.2	1176.7	1147.6	1114.8
15°	1439.7	1418.1	1400.2	1383.8	1375.6	1342.9	1319.0	1275.0	1224.4	1193.1	1170.7
17.5°	1508.3	1498.6	1468.1	1460.6	1449.4	1411.4	1373.4	1330.2	1286.2	1242.3	1181.9
20°	1563.4	1557.5	1537.4	1526.9	1509.0	1479.2	1433.0	1383.1	1332.4	1269.8	1213.2
22.5°	1587.3	1579.8	1563.4	1554.5	1543.3	1518.0	1478.5	1421.9	1355.5	1299.6	1239.3
25°	1540.3	1553.8	1549.3	1545.6	1541.1	1526.2	1496.4	1446.4	1381.6	1318.3	1243.0
27.5°	1434.5	1457.6	1480.0	1483.0	1490.4	1496.4	1484.4	1448.7	1394.3	1327.2	1244.5
30°	1292.2	1302.6	1348.1	1361.5	1371.9	1409.9	1432.3	1423.3	1381.6	1321.2	1245.2
32.5°	1109.6	1137.2	1183.4	1215.4	1243.7	1286.2	1344.3	1367.5	1352.5	1303.4	1228.1
35°	936.7	969.5	1023.2	1064.2	1092.5	1152.8	1221.4	1271.3	1289.9	1265.4	1198.3
37.5°	795.1	834.6	882.3	898.0	930.8	1005.3	1099.9	1169.2	1214.7	1216.9	1164.8
40°	688.6	708.7	746.7	770.5	802.6	865.2	957.6	1049.2	1117.8	1140.9	1113.3
42.5°	598.4	614.0	642.4	671.4	700.5	748.2	833.1	918.8	1011.2	1057.4	1056.7
45°	526.9	543.3	562.6	586.5	606.6	658.0	725.1	813.0	892.8	964.3	982.2
47.5°	464.3	478.4	502.3	512.7	526.1	574.6	632.7	714.7	797.4	879.3	900.2
50°	418.1	430.0	446.4	453.1	468.0	503.8	551.5	617.8	709.4	784.7	823.5
52.5°	376.3	385.3	397.9	403.2	413.6	440.4	483.6	535.8	611.8	689.3	743.7
55°	340.6	346.5	355.5	361.4	368.9	392.7	424.8	471.7	537.3	604.4	657.3
57.5°	307.0	311.5	320.4	323.4	329.4	348.0	370.4	409.9	470.2	529.8	581.3
60°	275.7	278.7	283.9	290.6	295.1	307.8	328.6	361.4	409.9	464.3	506.0
62.5°	245.9	250.4	251.9	254.9	258.6	270.5	286.9	310.8	353.2	397.9	441.9
65°	215.4	219.1	222.1	222.8	226.5	235.5	250.4	271.3	298.8	337.6	378.6
67.5°	187.0	189.3	190.8	193.8	197.5	202.0	213.9	229.5	254.9	286.2	318.9
70°	161.0	161.0	163.2	163.9	168.4	173.6	178.8	193.8	216.1	241.4	263.8
72.5°	132.6	136.4	135.6	139.4	138.6	142.3	149.0	158.7	175.1	195.2	216.9
75°	108.1	110.3	110.3	110.3	111.8	114.8	118.5	127.4	140.1	156.5	169.2
77.5°	84.2	85.7	85.7	85.7	86.4	89.4	93.2	99.1	108.1	117.7	125.2
80°	60.4	61.9	61.9	63.3	63.3	64.1	67.8	70.8	75.3	82.7	90.2
82.5°	41.0	41.7	43.2	43.2	42.5	44.0	44.7	47.7	52.2	53.7	58.9
85°	22.4	23.1	23.8	23.8	24.6	26.1	25.3	28.3	28.3	31.3	32.8
87.5°	8.9	10.4	10.4	9.7	10.4	10.4	10.4	11.9	12.7	13.4	12.7
90°	7.5	7.2	6.8	6.8	6.8	6.5	6.2	5.8	6.2	5.5	4.8
92.5°	32.5	34.9	40.0	44.2	48.5	61.5	82.4	111.4	134.0	117.3	85.1
95°	94.0	104.6	121.4	138.0	154.5	200.3	253.3	286.5	278.6	210.2	128.5
97.5°	218.8	239.3	262.5	281.6	300.8	338.4	364.8	359.3	298.1	201.4	117.3
100°	326.5	347.3	377.1	389.8	402.4	419.1	412.3	362.4	274.9	178.4	108.7
102.5°	424.9	438.6	454.0	457.4	460.8	450.6	409.9	336.7	245.8	163.1	106.3
105°	487.8	490.6	489.9	482.9	475.9	442.0	382.9	304.6	224.3	155.5	107.7
107.5°	510.7	504.6	489.5	475.2	460.8	413.6	349.7	278.3	210.2	153.5	111.8
110°	505.3	490.9	466.6	447.8	429.0	379.5	320.3	259.5	203.7	154.2	116.6

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	479.6	461.5	433.1	414.3	395.5	349.4	298.8	248.9	200.7	156.2	121.7
115°	448.2	427.7	400.7	384.2	367.8	327.8	285.8	243.1	200.0	159.0	127.2
117.5°	416.7	398.9	375.0	360.6	346.3	313.8	278.3	240.0	199.6	161.7	132.6
120°	391.4	376.4	356.9	344.8	332.6	305.3	273.5	237.6	199.6	164.8	138.5
122.5°	372.6	360.3	344.6	334.4	324.1	299.8	269.4	234.9	199.3	167.9	143.9
125°	360.0	350.1	336.4	327.0	317.6	294.0	264.6	231.8	199.0	170.9	149.4
127.5°	351.4	342.5	328.9	320.0	311.1	287.5	259.1	227.7	198.3	173.3	154.2
130°	343.2	334.7	320.7	311.6	302.5	279.3	252.3	223.9	197.9	176.1	158.6
132.5°	334.3	324.4	310.7	301.6	292.6	270.1	245.1	220.5	197.6	178.4	163.1
135°	322.0	312.5	298.8	290.2	281.7	260.8	238.6	217.1	197.3	180.8	166.8
137.5°	308.7	298.8	285.8	278.0	270.1	251.9	232.5	214.0	197.3	182.2	169.6
140°	292.6	285.1	273.1	266.0	258.8	243.4	227.3	211.6	196.9	183.9	172.3
142.5°	277.9	271.1	260.8	254.8	248.9	236.2	222.5	209.6	196.9	185.3	174.3
145°	263.9	258.1	249.6	244.8	240.0	229.7	218.1	207.2	196.2	185.6	175.7
147.5°	251.9	246.8	240.3	236.4	232.5	223.9	214.3	205.1	195.2	186.0	177.1
150°	241.7	237.2	231.8	228.7	225.6	218.8	210.9	202.7	194.2	186.0	178.1
152.5°	232.5	229.0	224.6	222.2	219.8	213.7	207.2	200.0	192.5	185.3	178.8
155°	224.3	221.5	218.1	216.0	214.0	208.9	203.4	197.3	190.8	184.6	179.1
157.5°	216.7	214.7	211.9	210.2	208.5	204.1	199.3	194.5	189.0	183.9	179.1
160°	209.9	207.8	205.8	204.4	203.1	199.3	195.5	191.4	187.0	182.9	179.1
162.5°	203.4	201.4	200.0	198.8	197.6	194.9	191.8	188.7	184.9	181.9	179.1
165°	197.3	195.9	194.5	193.6	192.8	190.4	188.4	185.6	182.9	180.5	178.4
167.5°	191.4	190.4	189.7	189.2	188.7	186.7	184.9	182.9	180.8	179.1	177.8
170°	186.3	186.0	185.3	184.8	184.3	182.9	181.9	180.2	178.8	177.8	177.1
172.5°	181.9	181.5	181.2	180.8	180.5	179.8	179.1	177.8	176.7	176.4	176.4
175°	178.4	177.8	177.8	177.8	177.8	177.1	176.7	176.1	175.4	175.4	175.7
177.5°	175.7	175.4	175.7	175.6	175.4	175.4	175.0	174.7	174.3	174.3	175.0
180°	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5
2.5°	927.8	924.8	922.6	922.6	915.9	909.1	905.4	903.9	902.4	896.5	888.3
5°	965.8	956.1	949.4	942.7	931.5	919.6	907.7	901.0	891.3	877.9	868.2
7.5°	1008.3	985.2	977.7	969.5	947.2	927.0	910.6	896.5	880.8	863.7	846.6
10°	1044.0	1019.4	1003.0	988.9	959.8	933.0	908.4	887.5	867.4	845.1	824.2
12.5°	1078.3	1043.3	1026.1	1005.3	974.7	936.0	903.9	877.9	848.0	824.9	799.6
15°	1126.0	1067.1	1038.8	1025.4	984.4	939.0	900.2	861.5	836.9	801.8	779.5
17.5°	1133.5	1085.8	1067.1	1032.9	983.7	932.3	887.5	848.8	811.5	780.2	751.2
20°	1159.5	1096.9	1067.1	1045.5	980.7	928.5	879.3	829.4	793.6	760.1	727.3
22.5°	1175.9	1105.1	1073.8	1039.6	977.7	915.1	857.0	813.8	769.8	735.5	709.4
25°	1171.5	1100.7	1065.6	1033.6	958.3	895.7	843.6	788.4	747.4	710.2	675.9
27.5°	1169.2	1089.5	1052.2	1016.5	945.7	880.1	814.5	769.8	724.3	681.1	655.8
30°	1163.3	1075.3	1032.1	993.4	919.6	851.0	795.1	743.0	697.5	658.0	624.5
32.5°	1143.1	1051.5	1009.8	968.0	891.3	822.7	766.1	717.6	672.2	631.2	599.1
35°	1116.3	1023.2	977.7	933.7	857.0	787.7	735.5	684.8	642.4	602.9	572.3
37.5°	1089.5	990.4	947.9	897.2	826.4	754.1	700.5	655.0	615.5	574.6	541.0
40°	1050.7	951.6	904.7	861.5	778.7	710.9	661.7	620.8	582.0	543.3	514.9
42.5°	997.8	909.1	860.7	813.0	735.5	668.4	620.8	584.2	547.7	515.7	484.4
45°	944.2	857.7	814.5	772.0	687.8	624.5	580.5	547.0	516.4	481.4	456.1
47.5°	879.3	806.3	763.1	721.4	641.6	578.3	538.0	506.7	478.4	449.4	425.5
50°	813.0	749.7	710.2	667.0	590.9	533.6	494.1	468.0	444.9	417.3	397.9
52.5°	741.5	686.3	652.8	611.1	544.0	491.1	450.8	424.8	405.4	385.3	368.1
55°	665.5	625.2	589.5	555.9	492.6	444.9	409.1	386.0	372.6	354.0	339.1
57.5°	596.9	558.2	536.5	498.5	443.4	396.4	368.1	348.8	333.1	321.9	310.0
60°	525.4	494.1	470.2	442.7	394.2	354.7	324.9	313.7	297.3	289.1	283.9
62.5°	456.8	434.5	412.1	391.2	348.0	310.8	288.4	274.2	264.5	256.4	251.9
65°	392.0	371.1	355.5	336.8	301.1	271.3	250.4	239.2	229.5	227.3	222.1
67.5°	328.6	319.7	302.6	287.6	257.1	234.0	218.3	204.2	199.0	196.7	192.3
70°	275.0	264.5	251.1	238.5	215.4	195.2	181.1	175.9	168.4	167.7	162.5
72.5°	226.5	213.9	204.2	194.5	177.4	159.5	152.0	144.6	140.8	137.9	135.6
75°	179.6	170.7	163.9	155.7	140.8	128.9	118.5	115.5	113.3	112.5	111.0
77.5°	134.1	128.2	125.2	117.0	106.6	96.1	91.7	87.2	87.2	85.7	86.4
80°	95.4	91.7	87.9	83.5	74.5	70.0	66.3	63.3	61.9	61.1	61.9
82.5°	60.4	58.1	57.4	54.4	48.4	46.2	43.2	41.0	41.0	41.0	41.0
85°	33.5	33.5	33.5	29.1	26.8	24.6	23.1	22.4	22.4	22.4	23.1
87.5°	14.2	14.2	11.9	11.9	11.2	9.7	8.9	8.9	9.7	9.7	10.4
90°	4.8	2.7	2.7	2.7	2.4	2.1	1.0	0.3	1.0	2.1	2.4
92.5°	52.0	30.8	26.4	21.9	15.7	10.6	6.8	4.8	6.8	10.6	15.7
95°	72.5	42.7	35.6	28.4	20.2	15.7	12.3	11.3	12.3	15.7	20.2
97.5°	69.1	45.5	39.4	33.2	26.0	21.9	18.8	18.8	18.8	21.9	26.0
100°	70.1	49.9	44.4	39.0	32.5	28.4	26.0	26.0	26.0	28.4	32.5
102.5°	73.5	55.7	50.6	45.5	39.3	35.6	33.5	32.8	33.5	35.6	39.3
105°	79.3	62.9	58.0	53.0	46.8	42.7	41.0	40.0	41.0	42.7	46.8
107.5°	85.5	70.4	65.4	60.5	54.7	50.3	48.5	47.9	48.5	50.3	54.7
110°	92.6	77.6	73.0	68.4	62.2	58.1	56.4	55.7	56.4	58.1	62.2

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	99.5	85.1	80.5	75.9	69.7	66.0	63.9	63.2	63.9	66.0	69.7
115°	106.7	93.0	88.4	83.8	77.3	73.8	71.4	70.4	71.4	73.8	77.3
117.5°	113.5	100.5	95.7	90.9	84.8	81.0	79.0	77.9	79.0	81.0	84.8
120°	120.7	107.7	102.9	98.1	92.3	88.5	86.1	85.5	86.1	88.5	92.3
122.5°	127.5	114.5	109.9	105.3	98.8	95.4	93.0	92.3	93.0	95.4	98.8
125°	133.7	121.4	116.6	111.8	105.3	101.5	99.5	98.1	99.5	101.5	105.3
127.5°	139.5	127.5	122.7	117.9	111.1	107.0	104.6	103.6	104.6	107.0	111.1
130°	145.3	133.7	128.8	123.8	117.3	112.1	109.4	108.0	109.4	112.1	117.3
132.5°	150.1	138.5	133.8	129.2	122.0	117.3	113.5	112.5	113.5	117.3	122.0
135°	154.5	143.2	138.8	134.3	127.2	121.4	117.9	116.6	117.9	121.4	127.2
137.5°	157.9	147.3	143.0	138.8	131.3	125.8	122.0	120.7	122.0	125.8	131.3
140°	161.4	151.1	147.0	142.9	135.7	129.9	126.1	125.1	126.1	129.9	135.7
142.5°	164.4	154.5	150.6	146.7	139.8	134.3	130.9	129.9	130.9	134.3	139.8
145°	166.5	157.6	153.8	150.1	143.6	138.8	135.4	134.3	135.4	138.8	143.6
147.5°	168.9	160.3	156.9	153.5	148.0	142.9	139.8	139.5	139.8	142.9	148.0
150°	170.6	163.1	159.8	156.6	151.4	147.3	144.6	144.3	144.6	147.3	151.4
152.5°	172.0	165.5	162.6	159.6	155.2	151.4	148.7	148.7	148.7	151.4	155.2
155°	173.3	167.5	165.0	162.4	158.6	155.2	153.2	152.8	153.2	155.2	158.6
157.5°	174.3	169.2	167.1	165.1	161.7	159.0	156.9	156.9	156.9	159.0	161.7
160°	175.0	170.9	169.0	167.2	164.4	162.0	160.7	160.7	160.7	162.0	164.4
162.5°	175.7	172.0	170.6	169.2	166.8	164.8	163.7	164.1	163.7	164.8	166.8
165°	175.7	172.6	171.6	170.6	168.9	167.2	166.5	166.5	166.5	167.2	168.9
167.5°	175.7	173.3	172.4	171.6	170.6	169.2	168.9	169.2	168.9	169.2	170.6
170°	175.4	173.7	173.1	172.6	172.0	170.9	170.6	170.9	170.6	170.9	172.0
172.5°	175.0	174.0	173.6	173.3	173.0	172.3	172.3	172.6	172.3	172.3	173.0
175°	174.7	174.0	174.0	174.0	173.7	173.3	173.3	173.7	173.3	173.3	173.7
177.5°	174.3	174.0	174.0	174.0	174.0	173.7	174.0	174.3	174.0	173.7	174.0
180°	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5
2.5°	886.0	883.1	884.6	877.1	870.4	860.7	852.5	851.0	849.5	854.0	851.0
5°	860.7	857.0	853.3	844.3	830.9	822.7	810.8	810.0	805.6	798.9	800.3
7.5°	833.1	830.9	825.7	811.5	799.6	785.4	775.8	767.6	763.8	757.9	755.6
10°	810.8	802.6	798.1	782.5	768.3	753.4	740.7	734.8	728.1	722.8	719.1
12.5°	780.2	778.0	765.3	752.7	740.7	723.6	713.9	696.8	687.8	692.3	690.8
15°	760.1	749.7	746.7	728.8	708.7	697.5	679.6	668.4	664.7	658.0	649.8
17.5°	733.3	726.6	716.1	699.7	676.6	661.0	648.3	637.9	633.4	624.5	617.8
20°	707.9	696.8	688.6	673.7	651.3	631.2	615.5	608.8	597.7	590.2	586.5
22.5°	684.8	676.6	664.7	642.4	623.0	603.6	585.0	575.3	564.9	560.4	554.4
25°	656.5	643.1	634.9	610.3	589.5	573.8	556.7	544.0	538.0	530.6	529.1
27.5°	629.0	616.3	606.6	585.0	559.6	539.5	529.1	520.2	509.7	509.7	506.0
30°	601.4	592.4	577.5	556.7	532.8	513.4	501.5	493.3	489.6	486.6	485.9
32.5°	573.8	561.9	552.9	524.6	506.7	488.9	479.9	473.2	468.7	468.0	468.7
35°	545.5	532.1	523.1	497.8	479.9	463.5	459.8	453.8	451.6	450.8	454.6
37.5°	515.7	505.2	494.1	473.2	453.1	443.4	435.9	433.7	433.0	437.4	438.9
40°	488.1	479.2	468.7	446.4	431.5	421.0	417.3	415.1	418.1	422.5	424.8
42.5°	462.0	449.4	441.2	421.0	407.6	401.7	397.2	397.2	400.2	405.4	409.1
45°	434.5	424.8	416.6	398.7	386.8	380.1	379.3	380.1	383.8	387.5	392.0
47.5°	407.6	397.9	389.0	374.1	363.7	359.9	359.2	359.9	365.9	371.1	376.3
50°	383.0	372.6	364.4	350.2	342.0	337.6	338.3	342.0	346.5	354.0	360.7
52.5°	354.0	346.5	339.1	326.4	318.9	316.0	318.2	321.2	329.4	334.6	342.8
55°	325.7	318.9	313.0	303.3	297.3	295.1	296.6	301.1	307.8	316.7	326.4
57.5°	299.6	292.1	286.2	279.5	272.7	273.5	274.2	280.2	288.4	296.6	307.8
60°	270.5	266.0	260.8	252.6	249.6	249.6	251.9	258.6	266.0	279.5	289.1
62.5°	244.4	238.5	234.7	229.5	225.1	225.8	231.0	237.0	245.9	257.1	269.8
65°	217.6	210.9	207.9	203.4	202.0	202.7	206.4	215.4	225.1	234.7	246.7
67.5°	187.8	185.6	182.6	178.1	179.6	180.3	184.1	191.5	202.0	211.6	225.1
70°	162.5	158.0	157.2	153.5	153.5	155.7	163.2	168.4	178.1	188.5	202.7
72.5°	135.6	131.9	131.9	128.9	131.2	133.4	137.1	144.6	153.5	163.9	175.9
75°	108.1	106.6	108.1	106.6	106.6	110.3	114.8	120.7	130.4	141.6	151.3
77.5°	83.5	83.5	82.7	85.0	85.0	87.2	93.2	99.1	106.6	115.5	125.9
80°	61.1	61.1	61.1	63.3	65.6	65.6	69.3	76.8	83.5	89.4	99.1
82.5°	41.7	41.7	41.7	43.2	46.2	46.2	50.7	55.1	62.6	67.8	72.3
85°	25.3	25.3	24.6	26.1	26.8	29.1	32.8	35.8	39.5	44.0	48.4
87.5°	11.2	11.2	11.9	12.7	13.4	14.9	16.4	17.9	21.6	23.1	25.3
90°	2.7	2.7	2.7	4.8	4.8	5.5	6.2	5.8	6.2	6.5	6.8
92.5°	21.9	26.4	30.8	52.0	85.1	117.3	134.0	111.4	82.4	61.5	48.5
95°	28.4	35.6	42.7	72.5	128.5	210.2	278.6	286.5	253.3	200.3	154.5
97.5°	33.2	39.4	45.5	69.1	117.3	201.4	298.1	359.3	364.8	338.4	300.8
100°	39.0	44.4	49.9	70.1	108.7	178.4	274.9	362.4	412.3	419.1	402.4
102.5°	45.5	50.6	55.7	73.5	106.3	163.1	245.8	336.7	409.9	450.6	460.8
105°	53.0	58.0	62.9	79.3	107.7	155.5	224.3	304.6	382.9	442.0	475.9
107.5°	60.5	65.4	70.4	85.5	111.8	153.5	210.2	278.3	349.7	413.6	460.8
110°	68.4	73.0	77.6	92.6	116.6	154.2	203.7	259.5	320.3	379.5	429.0

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	75.9	80.5	85.1	99.5	121.7	156.2	200.7	248.9	298.8	349.4	395.5
115°	83.8	88.4	93.0	106.7	127.2	159.0	200.0	243.1	285.8	327.8	367.8
117.5°	90.9	95.7	100.5	113.5	132.6	161.7	199.6	240.0	278.3	313.8	346.3
120°	98.1	102.9	107.7	120.7	138.5	164.8	199.6	237.6	273.5	305.3	332.6
122.5°	105.3	109.9	114.5	127.5	143.9	167.9	199.3	234.9	269.4	299.8	324.1
125°	111.8	116.6	121.4	133.7	149.4	170.9	199.0	231.8	264.6	294.0	317.6
127.5°	117.9	122.7	127.5	139.5	154.2	173.3	198.3	227.7	259.1	287.5	311.1
130°	123.8	128.8	133.7	145.3	158.6	176.1	197.9	223.9	252.3	279.3	302.5
132.5°	129.2	133.8	138.5	150.1	163.1	178.4	197.6	220.5	245.1	270.1	292.6
135°	134.3	138.8	143.2	154.5	166.8	180.8	197.3	217.1	238.6	260.8	281.7
137.5°	138.8	143.0	147.3	157.9	169.6	182.2	197.3	214.0	232.5	251.9	270.1
140°	142.9	147.0	151.1	161.4	172.3	183.9	196.9	211.6	227.3	243.4	258.8
142.5°	146.7	150.6	154.5	164.4	174.3	185.3	196.9	209.6	222.5	236.2	248.9
145°	150.1	153.8	157.6	166.5	175.7	185.6	196.2	207.2	218.1	229.7	240.0
147.5°	153.5	156.9	160.3	168.9	177.1	186.0	195.2	205.1	214.3	223.9	232.5
150°	156.6	159.8	163.1	170.6	178.1	186.0	194.2	202.7	210.9	218.8	225.6
152.5°	159.6	162.6	165.5	172.0	178.8	185.3	192.5	200.0	207.2	213.7	219.8
155°	162.4	165.0	167.5	173.3	179.1	184.6	190.8	197.3	203.4	208.9	214.0
157.5°	165.1	167.1	169.2	174.3	179.1	183.9	189.0	194.5	199.3	204.1	208.5
160°	167.2	169.0	170.9	175.0	179.1	182.9	187.0	191.4	195.5	199.3	203.1
162.5°	169.2	170.6	172.0	175.7	179.1	181.9	184.9	188.7	191.8	194.9	197.6
165°	170.6	171.6	172.6	175.7	178.4	180.5	182.9	185.6	188.4	190.4	192.8
167.5°	171.6	172.4	173.3	175.7	177.8	179.1	180.8	182.9	184.9	186.7	188.7
170°	172.6	173.1	173.7	175.4	177.1	177.8	178.8	180.2	181.9	182.9	184.3
172.5°	173.3	173.6	174.0	175.0	176.4	176.4	176.7	177.8	179.1	179.8	180.5
175°	174.0	174.0	174.0	174.7	175.7	175.4	175.4	176.1	176.7	177.1	177.8
177.5°	174.0	174.0	174.0	174.3	175.0	174.3	174.3	174.7	175.0	175.4	175.4
180°	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5
2.5°	848.8	848.0	844.3	845.8	841.3	842.8	845.1	845.8	848.8	846.6	845.8
5°	796.6	795.1	792.9	790.7	789.9	792.9	787.7	789.2	790.7	792.9	795.9
7.5°	754.1	753.4	751.2	747.4	745.9	744.5	745.2	750.4	749.7	748.9	754.1
10°	715.4	716.1	711.7	710.9	706.5	705.7	706.5	707.9	710.2	713.2	713.9
12.5°	675.2	684.8	676.6	673.7	667.0	670.7	672.2	665.5	669.2	671.4	682.6
15°	649.8	645.3	640.1	640.1	637.1	635.7	631.9	637.1	640.1	644.6	643.1
17.5°	614.8	607.3	604.4	601.4	602.1	605.1	596.9	608.8	608.8	611.1	607.3
20°	584.2	578.3	574.6	573.1	570.8	569.3	568.6	571.6	576.0	577.5	581.3
22.5°	552.2	552.2	546.2	544.0	542.5	540.3	544.0	541.8	544.7	547.7	553.7
25°	525.4	525.4	523.1	520.2	517.9	516.4	518.7	517.9	520.2	523.9	525.4
27.5°	503.8	501.5	500.8	500.0	499.3	500.0	499.3	501.5	503.8	504.5	503.0
30°	485.1	482.9	483.6	483.6	484.4	483.6	482.9	485.1	485.9	484.4	485.1
32.5°	468.0	468.0	469.5	470.2	470.2	471.0	471.7	470.2	471.0	468.7	469.5
35°	453.8	455.3	456.8	457.6	458.3	457.6	459.0	458.3	456.8	455.3	454.6
37.5°	439.7	441.2	444.1	444.9	447.1	447.9	446.4	446.4	445.6	442.7	441.2
40°	424.8	426.3	430.0	432.2	433.7	435.9	434.5	434.5	431.5	428.5	426.3
42.5°	410.6	413.6	417.3	419.6	422.5	422.5	422.5	421.0	417.3	414.3	412.1
45°	396.4	397.2	402.4	406.1	409.1	409.1	409.1	406.9	404.6	398.7	395.7
47.5°	380.8	383.0	389.0	392.7	395.7	396.4	396.4	394.2	389.7	384.5	380.8
50°	363.7	367.4	374.1	379.3	383.0	384.5	382.3	380.8	375.6	369.6	365.2
52.5°	347.3	351.7	359.9	364.4	369.6	370.4	369.6	367.4	361.4	353.2	349.5
55°	330.9	334.6	343.5	351.0	355.5	357.0	355.5	351.7	344.3	336.1	332.4
57.5°	313.0	318.2	327.9	335.3	340.6	341.3	339.8	336.1	330.1	319.7	314.5
60°	294.4	301.1	310.8	318.2	324.9	325.7	324.2	318.9	311.5	301.1	296.6
62.5°	275.7	280.9	292.1	300.3	305.5	309.3	306.3	301.1	293.6	283.2	276.5
65°	254.1	261.6	271.3	278.7	284.7	285.4	283.9	279.5	271.3	260.1	254.9
67.5°	233.2	238.5	248.2	257.8	260.1	262.3	260.1	255.6	248.9	239.2	231.8
70°	207.9	212.4	224.3	231.0	234.0	236.2	234.7	230.3	224.3	215.4	209.4
72.5°	182.6	186.3	197.5	202.7	208.7	207.9	207.2	204.2	196.0	190.0	186.3
75°	155.7	160.2	167.7	174.4	176.6	176.6	176.6	174.4	169.2	159.5	155.7
77.5°	131.2	133.4	139.4	143.1	145.3	146.1	145.3	141.6	138.6	131.9	129.7
80°	100.6	106.6	111.0	111.8	114.8	114.8	114.8	113.3	110.3	103.6	102.8
82.5°	76.0	77.5	82.0	84.2	85.7	85.0	85.0	82.0	81.2	77.5	76.0
85°	51.4	53.7	52.9	55.9	56.6	55.1	55.1	56.6	52.9	53.7	51.4
87.5°	28.3	28.3	29.8	29.1	32.0	32.0	30.6	31.3	29.8	29.1	28.3
90°	6.8	6.8	7.2	7.5	7.2	7.2	7.2	7.5	7.2	6.8	6.8
92.5°	44.2	40.0	34.9	32.5	31.1	31.1	31.1	32.5	34.9	40.0	44.2
95°	138.0	121.4	104.6	94.0	87.9	83.4	87.9	94.0	104.6	121.4	138.0
97.5°	281.6	262.5	239.3	218.8	208.5	200.3	208.5	218.8	239.3	262.5	281.6
100°	389.8	377.1	347.3	326.5	316.2	313.5	316.2	326.5	347.3	377.1	389.8
102.5°	457.4	454.0	438.6	424.9	414.0	411.9	414.0	424.9	438.6	454.0	457.4
105°	482.9	489.9	490.6	487.8	483.0	481.0	483.0	487.8	490.6	489.9	482.9
107.5°	475.2	489.5	504.6	510.7	513.5	513.8	513.5	510.7	504.6	489.5	475.2
110°	447.8	466.6	490.9	505.3	511.4	514.5	511.4	505.3	490.9	466.6	447.8

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	414.3	433.1	461.5	479.6	488.9	494.3	488.9	479.6	461.5	433.1	414.3
115°	384.2	400.7	427.7	448.2	459.1	461.8	459.1	448.2	427.7	400.7	384.2
117.5°	360.6	375.0	398.9	416.7	428.3	430.1	428.3	416.7	398.9	375.0	360.6
120°	344.8	356.9	376.4	391.4	400.3	404.1	400.3	391.4	376.4	356.9	344.8
122.5°	334.4	344.6	360.3	372.6	379.8	383.6	379.8	372.6	360.3	344.6	334.4
125°	327.0	336.4	350.1	360.0	366.5	368.5	366.5	360.0	350.1	336.4	327.0
127.5°	320.0	328.9	342.5	351.4	356.9	358.9	356.9	351.4	342.5	328.9	320.0
130°	311.6	320.7	334.7	343.2	348.7	350.7	348.7	343.2	334.7	320.7	311.6
132.5°	301.6	310.7	324.4	334.3	339.5	341.5	339.5	334.3	324.4	310.7	301.6
135°	290.2	298.8	312.5	322.0	327.5	329.5	327.5	322.0	312.5	298.8	290.2
137.5°	278.0	285.8	298.8	308.7	313.1	315.5	313.1	308.7	298.8	285.8	278.0
140°	266.0	273.1	285.1	292.6	297.4	300.1	297.4	292.6	285.1	273.1	266.0
142.5°	254.8	260.8	271.1	277.9	282.0	283.7	282.0	277.9	271.1	260.8	254.8
145°	244.8	249.6	258.1	263.9	267.3	269.0	267.3	263.9	258.1	249.6	244.8
147.5°	236.4	240.3	246.8	251.9	254.7	255.4	254.7	251.9	246.8	240.3	236.4
150°	228.7	231.8	237.2	241.7	243.7	244.1	243.7	241.7	237.2	231.8	228.7
152.5°	222.2	224.6	229.0	232.5	233.5	233.8	233.5	232.5	229.0	224.6	222.2
155°	216.0	218.1	221.5	224.3	225.3	225.3	225.3	224.3	221.5	218.1	216.0
157.5°	210.2	211.9	214.7	216.7	217.4	217.4	217.4	216.7	214.7	211.9	210.2
160°	204.4	205.8	207.8	209.9	210.2	210.2	210.2	209.9	207.8	205.8	204.4
162.5°	198.8	200.0	201.4	203.4	203.7	203.4	203.7	203.4	201.4	200.0	198.8
165°	193.6	194.5	195.9	197.3	196.9	196.6	196.9	197.3	195.9	194.5	193.6
167.5°	189.2	189.7	190.4	191.4	191.4	191.1	191.4	191.4	190.4	189.7	189.2
170°	184.8	185.3	186.0	186.3	186.0	186.0	186.0	186.3	186.0	185.3	184.8
172.5°	180.8	181.2	181.5	181.9	181.5	180.8	181.5	181.9	181.5	181.2	180.8
175°	177.8	177.8	177.8	178.4	177.8	177.1	177.8	178.4	177.8	177.8	177.8
177.5°	175.6	175.7	175.4	175.7	175.0	174.3	175.0	175.7	175.4	175.7	175.6
180°	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5	899.5
2.5°	845.8	850.3	845.8	848.8	850.3	854.0	855.5	862.2	864.4	869.7	869.7
5°	795.1	797.4	798.1	801.1	804.1	811.5	816.7	826.4	837.6	839.1	845.8
7.5°	754.1	757.9	763.8	761.6	766.8	778.0	784.7	796.6	807.8	813.8	822.0
10°	717.6	722.1	724.3	726.6	736.3	745.9	756.4	764.6	779.5	788.4	795.1
12.5°	687.8	684.1	688.6	696.8	707.9	713.9	728.1	740.7	751.9	761.6	767.6
15°	649.1	652.1	656.5	670.7	673.7	688.6	693.8	707.9	728.8	737.8	745.2
17.5°	611.8	621.5	630.4	635.7	644.6	656.5	671.4	687.1	700.5	710.9	719.9
20°	582.0	591.7	596.9	600.6	609.6	626.0	640.1	659.5	676.6	684.8	696.8
22.5°	558.2	558.2	565.6	576.8	582.0	597.7	609.6	630.4	649.1	659.5	670.7
25°	528.3	532.8	538.8	548.5	555.9	568.6	585.7	603.6	623.7	632.7	646.8
27.5°	503.8	509.0	517.2	519.4	526.9	538.0	555.9	575.3	596.2	605.9	617.8
30°	485.1	488.1	491.1	495.6	502.3	512.0	526.9	544.0	569.3	576.8	591.7
32.5°	468.7	470.2	471.7	475.4	479.2	488.9	500.8	519.4	540.3	551.5	564.9
35°	453.8	452.3	453.1	455.3	459.0	462.8	475.4	491.1	510.5	523.9	534.3
37.5°	439.7	436.7	435.9	435.9	437.4	441.9	451.6	465.0	485.9	497.1	507.5
40°	424.0	421.0	419.6	418.8	418.1	421.0	428.5	441.9	458.3	468.7	480.7
42.5°	409.1	406.1	402.4	401.7	400.2	401.7	406.9	419.6	433.7	444.1	453.8
45°	394.2	389.0	384.5	381.5	382.3	380.1	383.8	393.5	409.9	416.6	426.3
47.5°	377.8	371.9	365.9	362.9	359.9	361.4	362.9	371.1	385.3	392.0	401.7
50°	362.2	354.0	347.3	343.5	341.3	339.8	341.3	349.5	359.9	365.9	374.1
52.5°	344.3	336.1	329.4	323.4	320.4	318.2	318.9	326.4	336.1	342.0	350.2
55°	327.9	317.5	308.5	301.1	298.8	298.1	297.3	302.6	310.8	316.7	323.4
57.5°	309.3	298.8	289.1	280.2	275.7	275.0	275.0	276.5	286.9	291.4	295.1
60°	290.6	279.5	269.0	260.8	254.1	251.9	251.1	254.1	259.3	263.8	269.0
62.5°	269.8	258.6	245.9	238.5	231.8	225.8	228.0	228.8	236.2	238.5	242.9
65°	249.6	237.0	226.5	214.6	207.2	203.4	202.0	203.4	209.4	210.1	213.1
67.5°	226.5	214.6	202.0	193.8	187.0	180.3	178.8	178.8	181.8	184.1	187.8
70°	204.2	192.3	178.1	169.2	162.5	156.5	154.3	153.5	155.7	157.2	161.0
72.5°	178.1	166.2	155.7	146.1	137.9	133.4	131.2	129.7	131.9	133.4	134.1
75°	150.5	140.8	130.4	120.7	115.5	111.0	108.1	105.8	107.3	107.3	107.3
77.5°	124.4	114.8	106.6	99.9	93.2	87.9	85.7	83.5	84.2	84.2	85.7
80°	96.9	90.2	83.5	77.5	71.5	67.1	65.6	63.3	61.9	61.1	61.1
82.5°	71.5	66.3	60.4	55.1	52.2	47.7	46.2	43.2	43.2	42.5	42.5
85°	47.7	44.7	38.8	35.0	32.8	30.6	29.1	27.6	25.3	25.3	24.6
87.5°	25.3	23.8	22.4	17.9	17.9	15.6	14.9	14.2	11.9	12.7	12.7
90°	6.8	6.5	6.2	5.8	6.2	5.5	4.8	4.8	2.7	2.7	2.7
92.5°	48.5	61.5	82.4	111.4	134.0	117.3	85.1	52.0	30.8	26.4	21.9
95°	154.5	200.3	253.3	286.5	278.6	210.2	128.5	72.5	42.7	35.6	28.4
97.5°	300.8	338.4	364.8	359.3	298.1	201.4	117.3	69.1	45.5	39.4	33.2
100°	402.4	419.1	412.3	362.4	274.9	178.4	108.7	70.1	49.9	44.4	39.0
102.5°	460.8	450.6	409.9	336.7	245.8	163.1	106.3	73.5	55.7	50.6	45.5
105°	475.9	442.0	382.9	304.6	224.3	155.5	107.7	79.3	62.9	58.0	53.0
107.5°	460.8	413.6	349.7	278.3	210.2	153.5	111.8	85.5	70.4	65.4	60.5
110°	429.0	379.5	320.3	259.5	203.7	154.2	116.6	92.6	77.6	73.0	68.4

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	395.5	349.4	298.8	248.9	200.7	156.2	121.7	99.5	85.1	80.5	75.9
115°	367.8	327.8	285.8	243.1	200.0	159.0	127.2	106.7	93.0	88.4	83.8
117.5°	346.3	313.8	278.3	240.0	199.6	161.7	132.6	113.5	100.5	95.7	90.9
120°	332.6	305.3	273.5	237.6	199.6	164.8	138.5	120.7	107.7	102.9	98.1
122.5°	324.1	299.8	269.4	234.9	199.3	167.9	143.9	127.5	114.5	109.9	105.3
125°	317.6	294.0	264.6	231.8	199.0	170.9	149.4	133.7	121.4	116.6	111.8
127.5°	311.1	287.5	259.1	227.7	198.3	173.3	154.2	139.5	127.5	122.7	117.9
130°	302.5	279.3	252.3	223.9	197.9	176.1	158.6	145.3	133.7	128.8	123.8
132.5°	292.6	270.1	245.1	220.5	197.6	178.4	163.1	150.1	138.5	133.8	129.2
135°	281.7	260.8	238.6	217.1	197.3	180.8	166.8	154.5	143.2	138.8	134.3
137.5°	270.1	251.9	232.5	214.0	197.3	182.2	169.6	157.9	147.3	143.0	138.8
140°	258.8	243.4	227.3	211.6	196.9	183.9	172.3	161.4	151.1	147.0	142.9
142.5°	248.9	236.2	222.5	209.6	196.9	185.3	174.3	164.4	154.5	150.6	146.7
145°	240.0	229.7	218.1	207.2	196.2	185.6	175.7	166.5	157.6	153.8	150.1
147.5°	232.5	223.9	214.3	205.1	195.2	186.0	177.1	168.9	160.3	156.9	153.5
150°	225.6	218.8	210.9	202.7	194.2	186.0	178.1	170.6	163.1	159.8	156.6
152.5°	219.8	213.7	207.2	200.0	192.5	185.3	178.8	172.0	165.5	162.6	159.6
155°	214.0	208.9	203.4	197.3	190.8	184.6	179.1	173.3	167.5	165.0	162.4
157.5°	208.5	204.1	199.3	194.5	189.0	183.9	179.1	174.3	169.2	167.1	165.1
160°	203.1	199.3	195.5	191.4	187.0	182.9	179.1	175.0	170.9	169.0	167.2
162.5°	197.6	194.9	191.8	188.7	184.9	181.9	179.1	175.7	172.0	170.6	169.2
165°	192.8	190.4	188.4	185.6	182.9	180.5	178.4	175.7	172.6	171.6	170.6
167.5°	188.7	186.7	184.9	182.9	180.8	179.1	177.8	175.7	173.3	172.4	171.6
170°	184.3	182.9	181.9	180.2	178.8	177.8	177.1	175.4	173.7	173.1	172.6
172.5°	180.5	179.8	179.1	177.8	176.7	176.4	176.4	175.0	174.0	173.6	173.3
175°	177.8	177.1	176.7	176.1	175.4	175.4	175.7	174.7	174.0	174.0	174.0
177.5°	175.4	175.4	175.0	174.7	174.3	174.3	175.0	174.3	174.0	174.0	174.0
180°	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	899.5	899.5	899.5	899.5
2.5°	874.9	882.3	889.0	899.5
5°	855.5	865.9	880.1	895.7
7.5°	833.1	849.5	868.2	889.8
10°	812.3	830.9	854.7	880.8
12.5°	790.7	813.0	839.1	867.4
15°	766.1	788.4	817.5	855.5
17.5°	743.7	770.5	801.8	842.1
20°	717.6	743.0	777.2	823.5
22.5°	694.5	723.6	761.6	801.8
25°	669.2	694.5	732.5	781.0
27.5°	643.9	675.2	711.7	758.6
30°	619.3	645.3	684.8	734.0
32.5°	592.4	623.7	660.3	706.5
35°	563.4	593.2	627.5	677.4
37.5°	537.3	566.4	601.4	645.3
40°	508.2	538.8	570.8	614.8
42.5°	479.9	507.5	539.5	579.8
45°	452.3	476.2	505.2	540.3
47.5°	424.0	444.1	471.0	502.3
50°	393.5	415.1	435.2	461.3
52.5°	365.2	383.8	400.2	421.8
55°	337.6	350.2	363.7	380.1
57.5°	308.5	318.2	327.9	345.0
60°	279.5	288.4	293.6	304.8
62.5°	251.1	254.9	261.6	268.3
65°	219.8	225.1	228.8	237.0
67.5°	191.5	193.8	197.5	202.7
70°	161.7	166.9	168.4	172.1
72.5°	136.4	138.6	140.1	140.8
75°	108.1	110.3	111.8	116.3
77.5°	85.0	84.2	87.2	87.9
80°	62.6	60.4	61.1	64.1
82.5°	41.0	41.7	41.0	41.0
85°	25.3	24.6	23.1	23.8
87.5°	11.2	11.2	10.4	10.4
90°	2.4	2.1	1.0	0.3
92.5°	15.7	10.6	6.8	4.8
95°	20.2	15.7	12.3	11.3
97.5°	26.0	21.9	18.8	18.8
100°	32.5	28.4	26.0	26.0
102.5°	39.3	35.6	33.5	32.8
105°	46.8	42.7	41.0	40.0
107.5°	54.7	50.3	48.5	47.9
110°	62.2	58.1	56.4	55.7

TEST NUMBER: P1025607

CATALOG NUMBER: S124DIP-B575D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	69.7	66.0	63.9	63.2
115°	77.3	73.8	71.4	70.4
117.5°	84.8	81.0	79.0	77.9
120°	92.3	88.5	86.1	85.5
122.5°	98.8	95.4	93.0	92.3
125°	105.3	101.5	99.5	98.1
127.5°	111.1	107.0	104.6	103.6
130°	117.3	112.1	109.4	108.0
132.5°	122.0	117.3	113.5	112.5
135°	127.2	121.4	117.9	116.6
137.5°	131.3	125.8	122.0	120.7
140°	135.7	129.9	126.1	125.1
142.5°	139.8	134.3	130.9	129.9
145°	143.6	138.8	135.4	134.3
147.5°	148.0	142.9	139.8	139.5
150°	151.4	147.3	144.6	144.3
152.5°	155.2	151.4	148.7	148.7
155°	158.6	155.2	153.2	152.8
157.5°	161.7	159.0	156.9	156.9
160°	164.4	162.0	160.7	160.7
162.5°	166.8	164.8	163.7	164.1
165°	168.9	167.2	166.5	166.5
167.5°	170.6	169.2	168.9	169.2
170°	172.0	170.9	170.6	170.9
172.5°	173.0	172.3	172.3	172.6
175°	173.7	173.3	173.3	173.7
177.5°	174.0	173.7	174.0	174.3
180°	174.0	174.0	174.0	174.0

(END OF REPORT)