

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025641

Luminaire Tested: S124DIP-B575D590UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025641
REPORT IS A COMBINATION OF REPORTS P996241 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D590UB40-4F0-XX-W2A-A
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4919.0 lumens
Efficiency: N/A
Efficacy: 124.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	99	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	83	77	71	83	77	71	67	66	62	58	55	52	50	46	44	42
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	37	34	31
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	27
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19
9	51	39	31	26	47	36	30	25	32	26	23	28	23	20	23	20	18
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7583	7583	7583	7583
5°	7564	8699	7607	6536
10°	7507	10149	7565	5735
15°	7417	11701	7469	5132
20°	7321	12687	7374	4600
25°	7181	12542	7249	4209
30°	7044	10366	7130	4007
35°	6851	7725	6927	3884
40°	6627	5819	6692	3825
45°	6285	4670	6362	3744
50°	5875	3935	5960	3705
55°	5393	3425	5478	3661
60°	4926	3016	5069	3601
65°	4487	2595	4529	3451
70°	3971	2135	4056	3177
75°	3464	1640	3441	2700
80°	2727	1078	2694	2049
85°	1797	484	1681	1195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 9805 cd/sqm

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.5	1.8
10°-20°	279.3	5.7
20°-30°	443.8	9.0
30°-40°	493.1	10.0
40°-50°	448.4	9.1
50°-60°	366.4	7.4
60°-70°	261.6	5.3
70°-80°	143.9	2.9
80°-90°	40.5	0.8
90°-100°	25.2	0.5
100°-110°	166.1	3.4
110°-120°	317.2	6.4
120°-130°	402.7	8.2
130°-140°	430.8	8.8
140°-150°	402.8	8.2
150°-160°	324.8	6.6
160°-170°	209.5	4.3
170°-180°	72.2	1.5
0°-30°	813.6	16.5
0°-40°	1306.7	26.6
0°-60°	2121.6	43.1
0°-90°	2567.6	52.2
90°-120°	508.5	10.3
90°-150°	1744.9	35.5
90°-180°	2351.0	47.8
0°-180°	4919.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	930	930	930	930	930	
5°	926	1091	931	820	926	88
15°	884	1498	891	657	884	250
25°	807	1591	815	534	807	372
35°	700	941	708	473	700	437
45°	559	528	566	423	559	431
55°	393	345	399	369	393	353
65°	245	222	247	295	245	242
75°	120	111	119	183	120	126
85°	25	23	23	57	25	29
90°	2	17	2	17	2	3
95°	31	16	31	16	31	39
105°	171	162	171	162	171	179
115°	319	322	319	322	319	314
125°	449	452	449	452	449	401
135°	557	561	557	561	557	429
145°	642	646	642	646	642	401
155°	704	704	704	704	704	325
165°	743	739	743	739	743	210
175°	760	755	760	755	760	72
180°	760	760	760	760	760	

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9
2.5°	929.9	939.1	943.0	946.1	956.1	959.2	959.9	964.6	968.4	969.2	969.2
5°	926.1	940.7	952.2	963.0	979.2	986.1	994.6	1003.9	1016.2	1023.9	1027.7
7.5°	919.9	941.5	959.2	977.7	1000.0	1013.9	1021.6	1046.2	1063.2	1077.1	1094.0
10°	910.6	938.4	963.8	990.8	1022.4	1039.3	1056.3	1086.3	1110.2	1137.1	1158.7
12.5°	896.8	933.0	963.8	1001.6	1040.8	1060.9	1080.9	1133.3	1161.0	1184.9	1223.4
15°	884.4	920.7	964.6	1003.1	1051.6	1081.7	1111.0	1144.9	1188.8	1240.4	1277.4
17.5°	870.6	916.0	956.9	1010.8	1064.7	1093.2	1117.1	1169.5	1231.1	1282.0	1315.9
20°	851.3	897.5	951.5	1008.5	1072.4	1094.8	1126.4	1196.5	1251.9	1302.0	1357.5
22.5°	829.0	882.9	939.9	994.6	1060.9	1107.9	1142.5	1204.2	1271.2	1329.0	1391.4
25°	807.4	866.0	916.0	990.8	1060.9	1092.5	1131.8	1204.9	1278.1	1348.2	1412.2
27.5°	784.3	839.0	906.8	966.1	1045.5	1080.1	1122.5	1202.6	1280.4	1350.6	1419.1
30°	758.9	817.4	873.7	943.8	1020.8	1065.5	1104.8	1191.8	1271.2	1344.4	1408.3
32.5°	730.4	785.8	845.9	912.2	993.1	1038.5	1087.8	1177.2	1262.0	1325.1	1374.4
35°	700.3	756.6	808.9	876.7	959.9	1005.4	1053.2	1151.8	1235.8	1287.4	1315.9
37.5°	667.2	720.3	772.0	839.0	922.2	970.7	1019.3	1114.8	1194.2	1237.3	1229.6
40°	635.6	683.4	731.1	794.3	881.4	933.0	975.4	1071.7	1141.0	1159.5	1134.1
42.5°	599.4	640.2	686.4	751.2	835.9	884.4	937.6	1025.4	1077.1	1069.3	1026.2
45°	558.6	594.8	641.0	701.9	788.1	838.2	882.9	966.1	1003.9	984.6	906.0
47.5°	519.3	554.7	592.5	653.3	737.3	779.7	825.1	899.9	921.4	880.6	802.0
50°	476.9	506.2	545.5	603.2	681.8	726.5	764.3	824.4	832.1	782.0	700.3
52.5°	436.1	460.7	498.5	555.5	628.7	664.1	701.1	754.2	748.1	696.5	617.9
55°	392.9	416.0	450.7	503.1	567.8	601.7	633.3	680.3	667.2	614.0	545.5
57.5°	356.7	372.9	406.8	455.3	508.5	545.5	572.4	609.4	589.4	536.2	472.3
60°	315.1	335.1	363.6	402.9	455.3	480.0	503.9	528.5	514.6	463.8	406.8
62.5°	277.4	292.8	317.4	355.2	396.0	418.3	443.8	459.2	445.3	398.3	350.5
65°	245.0	257.3	276.6	307.4	346.7	365.2	379.8	394.5	382.9	339.0	304.3
67.5°	209.6	220.3	236.5	261.2	294.3	307.4	321.3	331.3	318.2	288.9	255.0
70°	178.0	185.7	201.1	219.6	242.7	255.0	266.6	276.6	265.0	240.4	214.9
72.5°	145.6	151.8	165.6	178.7	199.5	208.0	216.5	224.2	220.3	197.2	176.4
75°	120.2	122.5	131.7	142.5	155.6	164.9	171.0	175.7	172.6	154.1	141.0
77.5°	90.9	94.0	100.9	109.4	121.0	126.3	130.2	134.8	131.0	116.3	107.1
80°	66.3	67.0	70.9	78.6	86.3	87.1	90.9	97.1	94.8	84.7	77.8
82.5°	42.4	44.7	46.2	50.8	56.2	57.8	60.1	61.6	60.9	54.7	52.4
85°	24.7	24.7	26.2	29.3	30.8	33.1	33.9	34.7	36.2	32.4	30.0
87.5°	10.8	11.6	11.6	12.3	13.9	13.9	14.6	15.4	16.2	15.4	13.1
90°	1.7	3.1	4.5	5.9	7.3	8.0	8.5	9.5	10.5	11.5	12.5
92.5°	8.5	8.3	8.0	7.8	7.5	7.4	7.9	8.9	9.9	10.9	11.9
95°	31.3	27.0	22.7	18.4	14.1	11.9	12.0	12.1	12.2	12.4	12.5
97.5°	59.7	62.5	65.3	68.0	70.8	72.2	65.6	52.3	39.0	25.8	12.5
100°	93.2	95.5	97.7	100.0	102.3	103.4	94.7	77.3	59.8	42.4	25.0
102.5°	130.7	132.2	133.7	135.2	136.7	137.5	138.3	139.8	141.3	142.9	144.4
105°	171.1	171.9	172.6	173.4	174.1	174.5	174.8	175.4	176.1	176.7	177.3
107.5°	208.0	208.4	208.8	209.1	209.5	209.7	210.1	211.0	211.9	212.8	213.7
110°	245.5	245.9	246.3	246.6	247.0	247.2	247.6	248.4	249.1	249.9	250.7

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	281.9	282.7	283.4	284.2	284.9	285.3	285.4	285.7	286.0	286.2	286.5
115°	319.4	319.8	320.2	320.5	320.9	321.1	321.0	320.9	320.8	320.7	320.6
117.5°	353.0	353.5	354.0	354.5	355.0	355.2	355.4	355.8	356.1	356.5	356.9
120°	387.1	387.6	388.1	388.6	389.1	389.3	389.2	389.1	389.0	388.9	388.8
122.5°	418.9	419.1	419.4	419.6	419.9	420.0	420.1	420.4	420.7	420.9	421.2
125°	449.0	449.5	450.0	450.5	451.0	451.3	451.2	450.9	450.6	450.4	450.1
127.5°	478.0	478.1	478.3	478.4	478.5	478.6	478.9	479.5	480.2	480.8	481.4
130°	505.8	505.9	506.1	506.2	506.3	506.4	506.6	507.0	507.3	507.7	508.1
132.5°	531.4	531.7	531.9	532.2	532.5	532.6	532.8	533.3	533.8	534.3	534.8
135°	557.0	556.9	556.7	556.6	556.5	556.4	556.7	557.2	557.7	558.2	558.7
137.5°	579.7	579.7	579.7	579.7	579.7	579.7	580.0	580.7	581.3	582.0	582.6
140°	601.9	602.1	602.4	602.6	602.9	603.0	603.1	603.4	603.7	603.9	604.2
142.5°	621.8	622.3	622.8	623.3	623.8	624.1	624.2	624.3	624.4	624.5	624.6
145°	642.3	642.7	643.1	643.4	643.8	644.0	644.0	644.0	644.0	644.0	644.0
147.5°	658.2	659.0	659.7	660.5	661.2	661.6	661.5	661.4	661.3	661.1	661.0
150°	675.8	676.3	676.8	677.3	677.8	678.1	678.0	677.9	677.8	677.6	677.5
152.5°	690.6	691.0	691.4	691.7	692.1	692.3	692.2	691.9	691.6	691.4	691.1
155°	704.2	704.3	704.5	704.6	704.7	704.8	704.6	704.2	703.9	703.5	703.1
157.5°	716.1	716.1	716.1	716.1	716.1	716.1	715.9	715.4	714.9	714.4	713.9
160°	726.4	726.0	725.6	725.3	724.9	724.7	724.6	724.5	724.4	724.2	724.1
162.5°	735.5	735.0	734.5	734.0	733.5	733.2	733.1	733.0	732.9	732.7	732.6
165°	742.9	742.3	741.6	741.0	740.3	740.0	740.0	740.0	740.0	740.0	740.0
167.5°	749.1	748.5	747.9	747.2	746.6	746.3	746.2	746.1	746.0	745.8	745.7
170°	754.2	753.4	752.7	751.9	751.2	750.8	750.9	751.0	751.1	751.3	751.4
172.5°	757.6	756.8	756.1	755.3	754.6	754.2	754.3	754.4	754.5	754.7	754.8
175°	759.9	759.1	758.4	757.6	756.9	756.5	756.6	756.7	756.8	757.0	757.1
177.5°	761.6	760.7	759.8	758.9	758.0	757.6	757.7	758.0	758.3	758.5	758.8
180°	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9
2.5°	971.5	985.4	991.5	993.1	1001.6	996.2	998.5	997.7	1003.9	1004.6	1004.6
5°	1042.4	1058.6	1064.0	1071.7	1083.2	1086.3	1084.0	1088.6	1097.1	1090.9	1100.2
7.5°	1117.1	1134.8	1147.2	1164.1	1168.0	1178.0	1184.1	1189.5	1191.1	1191.8	1193.4
10°	1186.5	1208.8	1225.7	1254.3	1260.4	1265.8	1292.8	1282.0	1295.9	1291.2	1292.8
12.5°	1242.7	1286.6	1300.5	1348.2	1352.9	1371.4	1369.8	1386.8	1389.8	1396.0	1389.8
15°	1316.7	1367.5	1389.8	1416.8	1432.2	1453.8	1457.6	1480.8	1490.0	1498.5	1490.0
17.5°	1384.5	1411.4	1468.4	1490.0	1500.0	1511.6	1540.8	1549.3	1563.2	1557.8	1573.2
20°	1418.4	1456.9	1517.0	1553.9	1569.4	1580.1	1604.8	1617.9	1623.3	1623.3	1624.8
22.5°	1448.4	1503.9	1548.6	1590.9	1604.8	1612.5	1627.1	1637.2	1639.5	1641.0	1642.5
25°	1475.4	1525.4	1561.7	1585.5	1590.9	1590.9	1599.4	1593.2	1583.2	1590.9	1595.6
27.5°	1475.4	1510.8	1527.0	1535.5	1535.5	1514.7	1502.3	1476.9	1455.3	1449.2	1463.0
30°	1450.7	1466.9	1444.5	1423.7	1407.6	1393.7	1345.2	1306.6	1298.9	1293.5	1314.3
32.5°	1393.7	1372.9	1329.0	1268.9	1245.0	1213.4	1175.7	1146.4	1128.7	1122.5	1117.9
35°	1292.8	1238.8	1181.8	1100.9	1084.0	1043.9	992.3	970.7	941.5	940.7	950.7
37.5°	1182.6	1099.4	1037.8	960.7	936.8	894.5	845.9	823.6	803.6	788.1	806.6
40°	1053.9	981.5	887.5	824.4	790.5	768.1	727.3	702.6	693.4	685.7	697.2
42.5°	933.8	854.4	781.2	716.5	688.8	663.3	636.4	612.5	605.6	604.8	613.3
45°	814.3	736.5	668.7	613.3	595.5	580.1	553.9	547.0	535.4	527.7	531.6
47.5°	718.8	638.7	582.4	540.1	524.7	511.6	494.6	483.1	473.0	470.0	474.6
50°	624.8	570.9	513.1	477.7	466.1	453.8	440.7	429.9	425.3	422.2	425.3
52.5°	549.3	491.5	452.2	423.7	412.2	402.9	393.7	389.1	382.9	384.4	387.5
55°	481.5	430.7	397.5	376.7	369.8	366.0	354.4	349.0	346.7	345.2	346.7
57.5°	417.6	380.6	355.9	338.2	329.0	326.7	317.4	317.4	315.1	312.8	313.6
60°	366.7	335.1	311.3	297.4	295.8	292.0	285.8	285.1	279.7	282.0	282.7
62.5°	315.1	289.7	273.5	265.0	259.6	258.1	254.2	253.5	251.2	251.9	250.4
65°	274.3	253.5	237.3	230.4	228.0	227.3	224.2	221.9	220.3	221.9	220.3
67.5°	233.4	219.6	207.2	200.3	197.2	196.5	194.1	192.6	193.4	191.1	192.6
70°	194.9	181.0	173.3	169.5	168.0	165.6	165.6	165.6	165.6	164.1	163.3
72.5°	164.1	150.2	144.8	142.5	141.0	140.2	137.9	138.7	137.9	137.1	140.2
75°	130.2	121.7	116.3	114.0	115.6	113.3	110.9	112.5	110.2	110.9	114.0
77.5°	98.6	94.8	91.7	90.1	88.6	87.1	87.1	85.5	85.5	85.5	85.5
80°	71.6	70.9	65.5	64.7	64.7	63.2	63.2	63.2	63.2	62.4	63.2
82.5°	47.8	47.0	45.5	44.7	43.1	43.9	43.9	42.4	42.4	41.6	42.4
85°	27.7	27.7	26.2	25.4	24.7	25.4	23.9	23.1	23.9	23.1	23.9
87.5°	13.1	11.6	12.3	11.6	10.0	10.8	9.2	10.0	9.2	8.5	10.0
90°	13.3	14.0	14.8	15.5	15.9	16.0	16.3	16.6	16.8	17.1	16.8
92.5°	12.7	13.4	14.2	14.9	15.3	15.3	15.3	15.3	15.3	15.3	15.3
95°	13.3	14.0	14.8	15.5	15.9	16.0	16.1	16.2	16.4	16.5	16.4
97.5°	13.1	13.7	14.4	15.0	15.3	15.4	15.5	15.6	15.8	15.9	15.8
100°	22.8	20.7	18.5	16.4	15.3	15.4	15.5	15.6	15.8	15.9	15.8
102.5°	116.0	87.6	59.1	30.7	16.5	16.5	16.5	16.5	16.5	16.5	16.5
105°	178.4	179.6	180.7	181.8	182.4	180.1	175.6	171.1	166.5	162.0	166.5
107.5°	214.3	214.9	215.6	216.2	216.5	216.8	217.3	217.8	218.3	218.8	218.3
110°	250.9	251.2	251.4	251.7	251.8	252.0	252.4	252.7	253.1	253.5	253.1

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	286.4	286.2	286.1	286.0	285.9	286.2	286.7	287.2	287.7	288.2	287.7
115°	320.8	321.1	321.3	321.6	321.7	321.7	321.7	321.7	321.7	321.7	321.7
117.5°	356.8	356.7	356.6	356.5	356.4	356.4	356.4	356.4	356.4	356.4	356.4
120°	389.0	389.3	389.5	389.8	389.9	389.8	389.5	389.3	389.0	388.8	389.0
122.5°	421.3	421.4	421.5	421.6	421.7	421.6	421.3	421.1	420.8	420.6	420.8
125°	450.5	450.9	451.3	451.7	451.9	452.0	452.1	452.2	452.3	452.4	452.3
127.5°	481.3	481.1	481.0	480.9	480.8	480.7	480.6	480.5	480.4	480.3	480.4
130°	508.2	508.4	508.5	508.6	508.7	508.7	508.7	508.7	508.7	508.7	508.7
132.5°	534.9	535.1	535.2	535.3	535.4	535.3	535.2	535.1	534.9	534.8	534.9
135°	558.9	559.2	559.4	559.7	559.8	559.9	560.2	560.5	560.7	561.0	560.7
137.5°	582.8	583.1	583.3	583.6	583.7	583.6	583.5	583.4	583.2	583.1	583.2
140°	604.6	605.0	605.3	605.7	605.9	606.0	606.1	606.2	606.4	606.5	606.4
142.5°	624.9	625.1	625.4	625.7	625.8	625.8	625.8	625.8	625.8	625.8	625.8
145°	644.1	644.2	644.3	644.4	644.5	644.6	644.9	645.2	645.4	645.7	645.4
147.5°	661.1	661.3	661.4	661.5	661.6	661.7	661.8	661.9	662.1	662.2	662.1
150°	677.5	677.5	677.5	677.5	677.5	677.6	677.7	677.8	678.0	678.1	678.0
152.5°	691.4	691.6	691.9	692.2	692.3	692.2	692.1	692.0	691.8	691.7	691.8
155°	703.6	704.1	704.6	705.1	705.3	705.1	704.7	704.4	704.0	703.6	704.0
157.5°	714.5	715.1	715.8	716.4	716.7	716.4	715.8	715.1	714.5	713.9	714.5
160°	724.9	725.6	726.4	727.1	727.5	727.1	726.4	725.6	724.9	724.1	724.9
162.5°	733.4	734.1	734.9	735.6	736.0	735.6	734.7	733.8	733.0	732.1	733.0
165°	741.0	742.0	743.1	744.1	744.6	744.0	742.9	741.7	740.6	739.4	740.6
167.5°	746.8	748.0	749.1	750.2	750.8	750.2	748.9	747.6	746.4	745.1	746.4
170°	752.4	753.4	754.4	755.4	755.9	755.3	754.0	752.7	751.5	750.2	751.5
172.5°	755.8	756.8	757.8	758.8	759.3	758.6	757.2	755.9	754.5	753.1	754.5
175°	758.2	759.4	760.5	761.6	762.2	761.4	759.9	758.4	756.9	755.4	756.9
177.5°	759.8	760.8	761.8	762.8	763.3	762.5	761.0	759.5	758.0	756.5	758.0
180°	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9
2.5°	1003.1	1000.8	997.7	997.7	993.8	993.8	987.7	976.9	967.7	964.6	966.1
5°	1088.6	1089.4	1084.8	1080.9	1074.0	1068.6	1058.6	1039.3	1033.1	1020.8	1012.3
7.5°	1186.5	1183.4	1174.9	1168.7	1167.2	1154.9	1133.3	1110.2	1091.7	1079.4	1061.6
10°	1296.6	1284.3	1272.0	1268.1	1258.9	1238.1	1213.4	1188.0	1162.6	1135.6	1105.6
12.5°	1389.1	1365.2	1364.4	1355.2	1337.5	1325.9	1296.6	1260.4	1216.5	1186.5	1152.6
15°	1488.5	1466.1	1447.6	1430.7	1422.2	1388.3	1363.7	1318.2	1265.8	1233.5	1210.3
17.5°	1559.3	1549.3	1517.7	1510.0	1498.5	1459.2	1419.9	1375.2	1329.8	1284.3	1221.9
20°	1616.4	1610.2	1589.4	1578.6	1560.1	1529.3	1481.5	1429.9	1377.5	1312.8	1254.3
22.5°	1641.0	1633.3	1616.4	1607.1	1595.6	1569.4	1528.5	1470.0	1401.4	1343.6	1281.2
25°	1592.5	1606.3	1601.7	1597.9	1593.2	1577.8	1547.0	1495.4	1428.4	1362.9	1285.1
27.5°	1483.1	1507.0	1530.1	1533.1	1540.8	1547.0	1534.7	1497.7	1441.5	1372.1	1286.6
30°	1335.9	1346.7	1393.7	1407.6	1418.4	1457.6	1480.8	1471.5	1428.4	1366.0	1287.4
32.5°	1147.2	1175.7	1223.4	1256.6	1285.8	1329.8	1389.8	1413.7	1398.3	1347.5	1269.7
35°	968.4	1002.3	1057.8	1100.2	1129.4	1191.8	1262.7	1314.3	1333.6	1308.2	1238.8
37.5°	822.0	862.9	912.2	928.4	962.3	1039.3	1137.1	1208.8	1255.8	1258.1	1204.2
40°	711.9	732.7	772.0	796.6	829.7	894.5	990.0	1084.8	1155.6	1179.5	1151.0
42.5°	618.7	634.8	664.1	694.2	724.2	773.5	861.3	949.9	1045.5	1093.2	1092.5
45°	544.7	561.6	581.7	606.3	627.1	680.3	749.6	840.5	923.0	996.9	1015.4
47.5°	480.0	494.6	519.3	530.1	543.9	594.0	654.1	738.8	824.4	909.1	930.7
50°	432.2	444.5	461.5	468.4	483.8	520.8	570.1	638.7	733.4	811.3	851.3
52.5°	389.1	398.3	411.4	416.8	427.6	455.3	500.0	553.9	632.5	712.6	768.9
55°	352.1	358.2	367.5	373.7	381.4	406.0	439.1	487.7	555.5	624.8	679.5
57.5°	317.4	322.0	331.3	334.4	340.5	359.8	382.9	423.7	486.1	547.8	600.9
60°	285.1	288.1	293.5	300.5	305.1	318.2	339.8	373.7	423.7	480.0	523.1
62.5°	254.2	258.9	260.4	263.5	267.3	279.7	296.6	321.3	365.2	411.4	456.9
65°	222.7	226.5	229.6	230.4	234.2	243.5	258.9	280.4	308.9	349.0	391.4
67.5°	193.4	195.7	197.2	200.3	204.2	208.8	221.1	237.3	263.5	295.8	329.7
70°	166.4	166.4	168.7	169.5	174.1	179.5	184.9	200.3	223.4	249.6	272.7
72.5°	137.1	141.0	140.2	144.1	143.3	147.2	154.1	164.1	181.0	201.9	224.2
75°	111.7	114.0	114.0	114.0	115.6	118.6	122.5	131.7	144.8	161.8	174.9
77.5°	87.1	88.6	88.6	88.6	89.4	92.5	96.3	102.5	111.7	121.7	129.4
80°	62.4	63.9	63.9	65.5	65.5	66.3	70.1	73.2	77.8	85.5	93.2
82.5°	42.4	43.1	44.7	44.7	43.9	45.5	46.2	49.3	53.9	55.5	60.9
85°	23.1	23.9	24.7	24.7	25.4	27.0	26.2	29.3	29.3	32.4	33.9
87.5°	9.2	10.8	10.8	10.0	10.8	10.8	10.8	12.3	13.1	13.9	13.1
90°	16.6	16.3	16.0	15.9	15.5	14.8	14.0	13.3	12.5	11.5	10.5
92.5°	15.3	15.3	15.3	15.3	14.9	14.2	13.4	12.7	11.9	10.9	9.9
95°	16.2	16.1	16.0	15.9	15.5	14.8	14.0	13.3	12.5	12.4	12.2
97.5°	15.6	15.5	15.4	15.3	15.0	14.4	13.7	13.1	12.5	25.8	39.0
100°	15.6	15.5	15.4	15.3	16.4	18.5	20.7	22.8	25.0	42.4	59.8
102.5°	16.5	16.5	16.5	16.5	30.7	59.1	87.6	116.0	144.4	142.9	141.3
105°	171.1	175.6	180.1	182.4	181.8	180.7	179.6	178.4	177.3	176.7	176.1
107.5°	217.8	217.3	216.8	216.5	216.2	215.6	214.9	214.3	213.7	212.8	211.9
110°	252.7	252.4	252.0	251.8	251.7	251.4	251.2	250.9	250.7	249.9	249.1

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	287.2	286.7	286.2	285.9	286.0	286.1	286.2	286.4	286.5	286.2	286.0
115°	321.7	321.7	321.7	321.7	321.6	321.3	321.1	320.8	320.6	320.7	320.8
117.5°	356.4	356.4	356.4	356.4	356.5	356.6	356.7	356.8	356.9	356.5	356.1
120°	389.3	389.5	389.8	389.9	389.8	389.5	389.3	389.0	388.8	388.9	389.0
122.5°	421.1	421.3	421.6	421.7	421.6	421.5	421.4	421.3	421.2	420.9	420.7
125°	452.2	452.1	452.0	451.9	451.7	451.3	450.9	450.5	450.1	450.4	450.6
127.5°	480.5	480.6	480.7	480.8	480.9	481.0	481.1	481.3	481.4	480.8	480.2
130°	508.7	508.7	508.7	508.7	508.6	508.5	508.4	508.2	508.1	507.7	507.3
132.5°	535.1	535.2	535.3	535.4	535.3	535.2	535.1	534.9	534.8	534.3	533.8
135°	560.5	560.2	559.9	559.8	559.7	559.4	559.2	558.9	558.7	558.2	557.7
137.5°	583.4	583.5	583.6	583.7	583.6	583.3	583.1	582.8	582.6	582.0	581.3
140°	606.2	606.1	606.0	605.9	605.7	605.3	605.0	604.6	604.2	603.9	603.7
142.5°	625.8	625.8	625.8	625.8	625.7	625.4	625.1	624.9	624.6	624.5	624.4
145°	645.2	644.9	644.6	644.5	644.4	644.3	644.2	644.1	644.0	644.0	644.0
147.5°	661.9	661.8	661.7	661.6	661.5	661.4	661.3	661.1	661.0	661.1	661.3
150°	677.8	677.7	677.6	677.5	677.5	677.5	677.5	677.5	677.5	677.6	677.8
152.5°	692.0	692.1	692.2	692.3	692.2	691.9	691.6	691.4	691.1	691.4	691.6
155°	704.4	704.7	705.1	705.3	705.1	704.6	704.1	703.6	703.1	703.5	703.9
157.5°	715.1	715.8	716.4	716.7	716.4	715.8	715.1	714.5	713.9	714.4	714.9
160°	725.6	726.4	727.1	727.5	727.1	726.4	725.6	724.9	724.1	724.2	724.4
162.5°	733.8	734.7	735.6	736.0	735.6	734.9	734.1	733.4	732.6	732.7	732.9
165°	741.7	742.9	744.0	744.6	744.1	743.1	742.0	741.0	740.0	740.0	740.0
167.5°	747.6	748.9	750.2	750.8	750.2	749.1	748.0	746.8	745.7	745.8	746.0
170°	752.7	754.0	755.3	755.9	755.4	754.4	753.4	752.4	751.4	751.3	751.1
172.5°	755.9	757.2	758.6	759.3	758.8	757.8	756.8	755.8	754.8	754.7	754.5
175°	758.4	759.9	761.4	762.2	761.6	760.5	759.4	758.2	757.1	757.0	756.8
177.5°	759.5	761.0	762.5	763.3	762.8	761.8	760.8	759.8	758.8	758.5	758.3
180°	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9
2.5°	959.2	956.1	953.8	953.8	946.9	939.9	936.1	934.5	933.0	926.8	918.3
5°	998.5	988.5	981.5	974.6	963.0	950.7	938.4	931.4	921.4	907.6	897.5
7.5°	1042.4	1018.5	1010.8	1002.3	979.2	958.4	941.5	926.8	910.6	892.9	875.2
10°	1079.4	1053.9	1037.0	1022.4	992.3	964.6	939.1	917.6	896.8	873.7	852.1
12.5°	1114.8	1078.6	1060.9	1039.3	1007.7	967.7	934.5	907.6	876.7	852.9	826.7
15°	1164.1	1103.2	1074.0	1060.1	1017.7	970.7	930.7	890.6	865.2	829.0	805.9
17.5°	1171.8	1122.5	1103.2	1067.8	1017.0	963.8	917.6	877.5	839.0	806.6	776.6
20°	1198.8	1134.1	1103.2	1080.9	1013.9	959.9	909.1	857.5	820.5	785.8	751.9
22.5°	1215.7	1142.5	1110.2	1074.7	1010.8	946.1	886.0	841.3	795.8	760.4	733.4
25°	1211.1	1137.9	1101.7	1068.6	990.8	926.1	872.1	815.1	772.7	734.2	698.8
27.5°	1208.8	1126.4	1087.8	1050.9	977.7	909.9	842.1	795.8	748.9	704.2	678.0
30°	1202.6	1111.7	1067.0	1027.0	950.7	879.8	822.0	768.1	721.1	680.3	645.6
32.5°	1181.8	1087.1	1043.9	1000.8	921.4	850.5	792.0	741.9	694.9	652.5	619.4
35°	1154.1	1057.8	1010.8	965.3	886.0	814.3	760.4	708.0	664.1	623.3	591.7
37.5°	1126.4	1023.9	980.0	927.6	854.4	779.7	724.2	677.2	636.4	594.0	559.3
40°	1086.3	983.8	935.3	890.6	805.1	735.0	684.1	641.8	601.7	561.6	532.4
42.5°	1031.6	939.9	889.8	840.5	760.4	691.1	641.8	604.0	566.3	533.1	500.8
45°	976.1	886.8	842.1	798.2	711.1	645.6	600.2	565.5	533.9	497.7	471.5
47.5°	909.1	833.6	788.9	745.8	663.3	597.8	556.2	523.9	494.6	464.6	439.9
50°	840.5	775.0	734.2	689.5	610.9	551.6	510.8	483.8	459.9	431.4	411.4
52.5°	766.6	709.6	674.9	631.7	562.4	507.7	466.1	439.1	419.1	398.3	380.6
55°	688.0	646.4	609.4	574.7	509.3	459.9	423.0	399.1	385.2	366.0	350.5
57.5°	617.1	577.0	554.7	515.4	458.4	409.9	380.6	360.6	344.4	332.8	320.5
60°	543.1	510.8	486.1	457.6	407.6	366.7	335.9	324.3	307.4	298.9	293.5
62.5°	472.3	449.2	426.0	404.5	359.8	321.3	298.2	283.5	273.5	265.0	260.4
65°	405.2	383.7	367.5	348.2	311.3	280.4	258.9	247.3	237.3	235.0	229.6
67.5°	339.8	330.5	312.8	297.4	265.8	241.9	225.7	211.1	205.7	203.4	198.8
70°	284.3	273.5	259.6	246.5	222.7	201.9	187.2	181.8	174.1	173.3	168.0
72.5°	234.2	221.1	211.1	201.1	183.4	164.9	157.2	149.5	145.6	142.5	140.2
75°	185.7	176.4	169.5	161.0	145.6	133.3	122.5	119.4	117.1	116.3	114.8
77.5°	138.7	132.5	129.4	121.0	110.2	99.4	94.8	90.1	90.1	88.6	89.4
80°	98.6	94.8	90.9	86.3	77.0	72.4	68.6	65.5	63.9	63.2	63.9
82.5°	62.4	60.1	59.3	56.2	50.1	47.8	44.7	42.4	42.4	42.4	42.4
85°	34.7	34.7	34.7	30.0	27.7	25.4	23.9	23.1	23.1	23.1	23.9
87.5°	14.6	14.6	12.3	12.3	11.6	10.0	9.2	9.2	10.0	10.0	10.8
90°	9.5	8.5	8.0	7.3	5.9	4.5	3.1	1.7	3.1	4.5	5.9
92.5°	8.9	7.9	7.4	7.5	7.8	8.0	8.3	8.5	8.3	8.0	7.8
95°	12.1	12.0	11.9	14.1	18.4	22.7	27.0	31.3	27.0	22.7	18.4
97.5°	52.3	65.6	72.2	70.8	68.0	65.3	62.5	59.7	62.5	65.3	68.0
100°	77.3	94.7	103.4	102.3	100.0	97.7	95.5	93.2	95.5	97.7	100.0
102.5°	139.8	138.3	137.5	136.7	135.2	133.7	132.2	130.7	132.2	133.7	135.2
105°	175.4	174.8	174.5	174.1	173.4	172.6	171.9	171.1	171.9	172.6	173.4
107.5°	211.0	210.1	209.7	209.5	209.1	208.8	208.4	208.0	208.4	208.8	209.1
110°	248.4	247.6	247.2	247.0	246.6	246.3	245.9	245.5	245.9	246.3	246.6

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	285.7	285.4	285.3	284.9	284.2	283.4	282.7	281.9	282.7	283.4	284.2
115°	320.9	321.0	321.1	320.9	320.5	320.2	319.8	319.4	319.8	320.2	320.5
117.5°	355.8	355.4	355.2	355.0	354.5	354.0	353.5	353.0	353.5	354.0	354.5
120°	389.1	389.2	389.3	389.1	388.6	388.1	387.6	387.1	387.6	388.1	388.6
122.5°	420.4	420.1	420.0	419.9	419.6	419.4	419.1	418.9	419.1	419.4	419.6
125°	450.9	451.2	451.3	451.0	450.5	450.0	449.5	449.0	449.5	450.0	450.5
127.5°	479.5	478.9	478.6	478.5	478.4	478.3	478.1	478.0	478.1	478.3	478.4
130°	507.0	506.6	506.4	506.3	506.2	506.1	505.9	505.8	505.9	506.1	506.2
132.5°	533.3	532.8	532.6	532.5	532.2	531.9	531.7	531.4	531.7	531.9	532.2
135°	557.2	556.7	556.4	556.5	556.6	556.7	556.9	557.0	556.9	556.7	556.6
137.5°	580.7	580.0	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7
140°	603.4	603.1	603.0	602.9	602.6	602.4	602.1	601.9	602.1	602.4	602.6
142.5°	624.3	624.2	624.1	623.8	623.3	622.8	622.3	621.8	622.3	622.8	623.3
145°	644.0	644.0	644.0	643.8	643.4	643.1	642.7	642.3	642.7	643.1	643.4
147.5°	661.4	661.5	661.6	661.2	660.5	659.7	659.0	658.2	659.0	659.7	660.5
150°	677.9	678.0	678.1	677.8	677.3	676.8	676.3	675.8	676.3	676.8	677.3
152.5°	691.9	692.2	692.3	692.1	691.7	691.4	691.0	690.6	691.0	691.4	691.7
155°	704.2	704.6	704.8	704.7	704.6	704.5	704.3	704.2	704.3	704.5	704.6
157.5°	715.4	715.9	716.1	716.1	716.1	716.1	716.1	716.1	716.1	716.1	716.1
160°	724.5	724.6	724.7	724.9	725.3	725.6	726.0	726.4	726.0	725.6	725.3
162.5°	733.0	733.1	733.2	733.5	734.0	734.5	735.0	735.5	735.0	734.5	734.0
165°	740.0	740.0	740.0	740.3	741.0	741.6	742.3	742.9	742.3	741.6	741.0
167.5°	746.1	746.2	746.3	746.6	747.2	747.9	748.5	749.1	748.5	747.9	747.2
170°	751.0	750.9	750.8	751.2	751.9	752.7	753.4	754.2	753.4	752.7	751.9
172.5°	754.4	754.3	754.2	754.6	755.3	756.1	756.8	757.6	756.8	756.1	755.3
175°	756.7	756.6	756.5	756.9	757.6	758.4	759.1	759.9	759.1	758.4	757.6
177.5°	758.0	757.7	757.6	758.0	758.9	759.8	760.7	761.6	760.7	759.8	758.9
180°	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9
2.5°	916.0	913.0	914.5	906.8	899.9	889.8	881.4	879.8	878.3	882.9	879.8
5°	889.8	886.0	882.1	872.9	859.0	850.5	838.2	837.5	832.8	825.9	827.4
7.5°	861.3	859.0	853.6	839.0	826.7	812.0	802.0	793.5	789.7	783.5	781.2
10°	838.2	829.7	825.1	808.9	794.3	778.9	765.8	759.6	752.7	747.3	743.5
12.5°	806.6	804.3	791.2	778.1	765.8	748.1	738.1	720.3	711.1	715.7	714.2
15°	785.8	775.0	772.0	753.5	732.7	721.1	702.6	691.1	687.2	680.3	671.8
17.5°	758.1	751.2	740.4	723.4	699.5	683.4	670.3	659.5	654.9	645.6	638.7
20°	731.9	720.3	711.9	696.5	673.4	652.5	636.4	629.4	617.9	610.2	606.3
22.5°	708.0	699.5	687.2	664.1	644.1	624.0	604.8	594.8	584.0	579.4	573.2
25°	678.7	664.9	656.4	631.0	609.4	593.2	575.5	562.4	556.2	548.5	547.0
27.5°	650.2	637.1	627.1	604.8	578.6	557.8	547.0	537.8	527.0	527.0	523.1
30°	621.7	612.5	597.1	575.5	550.9	530.8	518.5	510.0	506.2	503.1	502.3
32.5°	593.2	580.9	571.7	542.4	523.9	505.4	496.2	489.2	484.6	483.8	484.6
35°	564.0	550.1	540.8	514.6	496.2	479.2	475.4	469.2	466.9	466.1	470.0
37.5°	533.1	522.3	510.8	489.2	468.4	458.4	450.7	448.4	447.6	452.2	453.8
40°	504.6	495.4	484.6	461.5	446.1	435.3	431.4	429.1	432.2	436.8	439.1
42.5°	477.7	464.6	456.1	435.3	421.4	415.3	410.6	410.6	413.7	419.1	423.0
45°	449.2	439.1	430.7	412.2	399.9	392.9	392.1	392.9	396.8	400.6	405.2
47.5°	421.4	411.4	402.2	386.8	376.0	372.1	371.3	372.1	378.3	383.7	389.1
50°	396.0	385.2	376.7	362.1	353.6	349.0	349.8	353.6	358.2	366.0	372.9
52.5°	366.0	358.2	350.5	337.4	329.7	326.7	329.0	332.1	340.5	345.9	354.4
55°	336.7	329.7	323.6	313.6	307.4	305.1	306.6	311.3	318.2	327.4	337.4
57.5°	309.7	302.0	295.8	288.9	282.0	282.7	283.5	289.7	298.2	306.6	318.2
60°	279.7	275.0	269.6	261.2	258.1	258.1	260.4	267.3	275.0	288.9	298.9
62.5°	252.7	246.5	242.7	237.3	232.7	233.4	238.8	245.0	254.2	265.8	278.9
65°	225.0	218.0	214.9	210.3	208.8	209.6	213.4	222.7	232.7	242.7	255.0
67.5°	194.1	191.8	188.8	184.1	185.7	186.4	190.3	198.0	208.8	218.8	232.7
70°	168.0	163.3	162.6	158.7	158.7	161.0	168.7	174.1	184.1	194.9	209.6
72.5°	140.2	136.4	136.4	133.3	135.6	137.9	141.8	149.5	158.7	169.5	181.8
75°	111.7	110.2	111.7	110.2	110.2	114.0	118.6	124.8	134.8	146.4	156.4
77.5°	86.3	86.3	85.5	87.8	87.8	90.1	96.3	102.5	110.2	119.4	130.2
80°	63.2	63.2	63.2	65.5	67.8	67.8	71.6	79.4	86.3	92.5	102.5
82.5°	43.1	43.1	43.1	44.7	47.8	47.8	52.4	57.0	64.7	70.1	74.7
85°	26.2	26.2	25.4	27.0	27.7	30.0	33.9	37.0	40.8	45.5	50.1
87.5°	11.6	11.6	12.3	13.1	13.9	15.4	16.9	18.5	22.3	23.9	26.2
90°	7.3	8.0	8.5	9.5	10.5	11.5	12.5	13.3	14.0	14.8	15.5
92.5°	7.5	7.4	7.9	8.9	9.9	10.9	11.9	12.7	13.4	14.2	14.9
95°	14.1	11.9	12.0	12.1	12.2	12.4	12.5	13.3	14.0	14.8	15.5
97.5°	70.8	72.2	65.6	52.3	39.0	25.8	12.5	13.1	13.7	14.4	15.0
100°	102.3	103.4	94.7	77.3	59.8	42.4	25.0	22.8	20.7	18.5	16.4
102.5°	136.7	137.5	138.3	139.8	141.3	142.9	144.4	116.0	87.6	59.1	30.7
105°	174.1	174.5	174.8	175.4	176.1	176.7	177.3	178.4	179.6	180.7	181.8
107.5°	209.5	209.7	210.1	211.0	211.9	212.8	213.7	214.3	214.9	215.6	216.2
110°	247.0	247.2	247.6	248.4	249.1	249.9	250.7	250.9	251.2	251.4	251.7

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	284.9	285.3	285.4	285.7	286.0	286.2	286.5	286.4	286.2	286.1	286.0
115°	320.9	321.1	321.0	320.9	320.8	320.7	320.6	320.8	321.1	321.3	321.6
117.5°	355.0	355.2	355.4	355.8	356.1	356.5	356.9	356.8	356.7	356.6	356.5
120°	389.1	389.3	389.2	389.1	389.0	388.9	388.8	389.0	389.3	389.5	389.8
122.5°	419.9	420.0	420.1	420.4	420.7	420.9	421.2	421.3	421.4	421.5	421.6
125°	451.0	451.3	451.2	450.9	450.6	450.4	450.1	450.5	450.9	451.3	451.7
127.5°	478.5	478.6	478.9	479.5	480.2	480.8	481.4	481.3	481.1	481.0	480.9
130°	506.3	506.4	506.6	507.0	507.3	507.7	508.1	508.2	508.4	508.5	508.6
132.5°	532.5	532.6	532.8	533.3	533.8	534.3	534.8	534.9	535.1	535.2	535.3
135°	556.5	556.4	556.7	557.2	557.7	558.2	558.7	558.9	559.2	559.4	559.7
137.5°	579.7	579.7	580.0	580.7	581.3	582.0	582.6	582.8	583.1	583.3	583.6
140°	602.9	603.0	603.1	603.4	603.7	603.9	604.2	604.6	605.0	605.3	605.7
142.5°	623.8	624.1	624.2	624.3	624.4	624.5	624.6	624.9	625.1	625.4	625.7
145°	643.8	644.0	644.0	644.0	644.0	644.0	644.0	644.1	644.2	644.3	644.4
147.5°	661.2	661.6	661.5	661.4	661.3	661.1	661.0	661.1	661.3	661.4	661.5
150°	677.8	678.1	678.0	677.9	677.8	677.6	677.5	677.5	677.5	677.5	677.5
152.5°	692.1	692.3	692.2	691.9	691.6	691.4	691.1	691.4	691.6	691.9	692.2
155°	704.7	704.8	704.6	704.2	703.9	703.5	703.1	703.6	704.1	704.6	705.1
157.5°	716.1	716.1	715.9	715.4	714.9	714.4	713.9	714.5	715.1	715.8	716.4
160°	724.9	724.7	724.6	724.5	724.4	724.2	724.1	724.9	725.6	726.4	727.1
162.5°	733.5	733.2	733.1	733.0	732.9	732.7	732.6	733.4	734.1	734.9	735.6
165°	740.3	740.0	740.0	740.0	740.0	740.0	740.0	741.0	742.0	743.1	744.1
167.5°	746.6	746.3	746.2	746.1	746.0	745.8	745.7	746.8	748.0	749.1	750.2
170°	751.2	750.8	750.9	751.0	751.1	751.3	751.4	752.4	753.4	754.4	755.4
172.5°	754.6	754.2	754.3	754.4	754.5	754.7	754.8	755.8	756.8	757.8	758.8
175°	756.9	756.5	756.6	756.7	756.8	757.0	757.1	758.2	759.4	760.5	761.6
177.5°	758.0	757.6	757.7	758.0	758.3	758.5	758.8	759.8	760.8	761.8	762.8
180°	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9
2.5°	877.5	876.7	872.9	874.4	869.8	871.4	873.7	874.4	877.5	875.2	874.4
5°	823.6	822.0	819.7	817.4	816.7	819.7	814.3	815.9	817.4	819.7	822.8
7.5°	779.7	778.9	776.6	772.7	771.2	769.7	770.4	775.8	775.0	774.3	779.7
10°	739.6	740.4	735.8	735.0	730.4	729.6	730.4	731.9	734.2	737.3	738.1
12.5°	698.0	708.0	699.5	696.5	689.5	693.4	694.9	688.0	691.8	694.2	705.7
15°	671.8	667.2	661.8	661.8	658.7	657.2	653.3	658.7	661.8	666.4	664.9
17.5°	635.6	627.9	624.8	621.7	622.5	625.6	617.1	629.4	629.4	631.7	627.9
20°	604.0	597.8	594.0	592.5	590.1	588.6	587.8	590.9	595.5	597.1	600.9
22.5°	570.9	570.9	564.7	562.4	560.9	558.6	562.4	560.1	563.2	566.3	572.4
25°	543.1	543.1	540.8	537.8	535.4	533.9	536.2	535.4	537.8	541.6	543.1
27.5°	520.8	518.5	517.7	517.0	516.2	517.0	516.2	518.5	520.8	521.6	520.0
30°	501.5	499.2	500.0	500.0	500.8	500.0	499.2	501.5	502.3	500.8	501.5
32.5°	483.8	483.8	485.4	486.1	486.1	486.9	487.7	486.1	486.9	484.6	485.4
35°	469.2	470.7	472.3	473.0	473.8	473.0	474.6	473.8	472.3	470.7	470.0
37.5°	454.6	456.1	459.2	459.9	462.3	463.0	461.5	461.5	460.7	457.6	456.1
40°	439.1	440.7	444.5	446.8	448.4	450.7	449.2	449.2	446.1	443.0	440.7
42.5°	424.5	427.6	431.4	433.7	436.8	436.8	436.8	435.3	431.4	428.4	426.0
45°	409.9	410.6	416.0	419.9	423.0	423.0	423.0	420.7	418.3	412.2	409.1
47.5°	393.7	396.0	402.2	406.0	409.1	409.9	409.9	407.6	402.9	397.5	393.7
50°	376.0	379.8	386.8	392.1	396.0	397.5	395.2	393.7	388.3	382.1	377.5
52.5°	359.0	363.6	372.1	376.7	382.1	382.9	382.1	379.8	373.7	365.2	361.3
55°	342.1	345.9	355.2	362.9	367.5	369.0	367.5	363.6	355.9	347.5	343.6
57.5°	323.6	329.0	339.0	346.7	352.1	352.9	351.3	347.5	341.3	330.5	325.1
60°	304.3	311.3	321.3	329.0	335.9	336.7	335.1	329.7	322.0	311.3	306.6
62.5°	285.1	290.5	302.0	310.5	315.9	319.7	316.6	311.3	303.5	292.8	285.8
65°	262.7	270.4	280.4	288.1	294.3	295.1	293.5	288.9	280.4	268.9	263.5
67.5°	241.1	246.5	256.6	266.6	268.9	271.2	268.9	264.3	257.3	247.3	239.6
70°	214.9	219.6	231.9	238.8	241.9	244.2	242.7	238.1	231.9	222.7	216.5
72.5°	188.8	192.6	204.2	209.6	215.7	214.9	214.2	211.1	202.6	196.5	192.6
75°	161.0	165.6	173.3	180.3	182.6	182.6	182.6	180.3	174.9	164.9	161.0
77.5°	135.6	137.9	144.1	147.9	150.2	151.0	150.2	146.4	143.3	136.4	134.1
80°	104.0	110.2	114.8	115.6	118.6	118.6	118.6	117.1	114.0	107.1	106.3
82.5°	78.6	80.1	84.7	87.1	88.6	87.8	87.8	84.7	84.0	80.1	78.6
85°	53.2	55.5	54.7	57.8	58.6	57.0	57.0	58.6	54.7	55.5	53.2
87.5°	29.3	29.3	30.8	30.0	33.1	33.1	31.6	32.4	30.8	30.0	29.3
90°	15.9	16.0	16.3	16.6	16.8	17.1	16.8	16.6	16.3	16.0	15.9
92.5°	15.3	15.3	15.3	15.3	15.3	15.3	15.3	15.3	15.3	15.3	15.3
95°	15.9	16.0	16.1	16.2	16.4	16.5	16.4	16.2	16.1	16.0	15.9
97.5°	15.3	15.4	15.5	15.6	15.8	15.9	15.8	15.6	15.5	15.4	15.3
100°	15.3	15.4	15.5	15.6	15.8	15.9	15.8	15.6	15.5	15.4	15.3
102.5°	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5
105°	182.4	180.1	175.6	171.1	166.5	162.0	166.5	171.1	175.6	180.1	182.4
107.5°	216.5	216.8	217.3	217.8	218.3	218.8	218.3	217.8	217.3	216.8	216.5
110°	251.8	252.0	252.4	252.7	253.1	253.5	253.1	252.7	252.4	252.0	251.8

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	285.9	286.2	286.7	287.2	287.7	288.2	287.7	287.2	286.7	286.2	285.9
115°	321.7	321.7	321.7	321.7	321.7	321.7	321.7	321.7	321.7	321.7	321.7
117.5°	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4	356.4
120°	389.9	389.8	389.5	389.3	389.0	388.8	389.0	389.3	389.5	389.8	389.9
122.5°	421.7	421.6	421.3	421.1	420.8	420.6	420.8	421.1	421.3	421.6	421.7
125°	451.9	452.0	452.1	452.2	452.3	452.4	452.3	452.2	452.1	452.0	451.9
127.5°	480.8	480.7	480.6	480.5	480.4	480.3	480.4	480.5	480.6	480.7	480.8
130°	508.7	508.7	508.7	508.7	508.7	508.7	508.7	508.7	508.7	508.7	508.7
132.5°	535.4	535.3	535.2	535.1	534.9	534.8	534.9	535.1	535.2	535.3	535.4
135°	559.8	559.9	560.2	560.5	560.7	561.0	560.7	560.5	560.2	559.9	559.8
137.5°	583.7	583.6	583.5	583.4	583.2	583.1	583.2	583.4	583.5	583.6	583.7
140°	605.9	606.0	606.1	606.2	606.4	606.5	606.4	606.2	606.1	606.0	605.9
142.5°	625.8	625.8	625.8	625.8	625.8	625.8	625.8	625.8	625.8	625.8	625.8
145°	644.5	644.6	644.9	645.2	645.4	645.7	645.4	645.2	644.9	644.6	644.5
147.5°	661.6	661.7	661.8	661.9	662.1	662.2	662.1	661.9	661.8	661.7	661.6
150°	677.5	677.6	677.7	677.8	678.0	678.1	678.0	677.8	677.7	677.6	677.5
152.5°	692.3	692.2	692.1	692.0	691.8	691.7	691.8	692.0	692.1	692.2	692.3
155°	705.3	705.1	704.7	704.4	704.0	703.6	704.0	704.4	704.7	705.1	705.3
157.5°	716.7	716.4	715.8	715.1	714.5	713.9	714.5	715.1	715.8	716.4	716.7
160°	727.5	727.1	726.4	725.6	724.9	724.1	724.9	725.6	726.4	727.1	727.5
162.5°	736.0	735.6	734.7	733.8	733.0	732.1	733.0	733.8	734.7	735.6	736.0
165°	744.6	744.0	742.9	741.7	740.6	739.4	740.6	741.7	742.9	744.0	744.6
167.5°	750.8	750.2	748.9	747.6	746.4	745.1	746.4	747.6	748.9	750.2	750.8
170°	755.9	755.3	754.0	752.7	751.5	750.2	751.5	752.7	754.0	755.3	755.9
172.5°	759.3	758.6	757.2	755.9	754.5	753.1	754.5	755.9	757.2	758.6	759.3
175°	762.2	761.4	759.9	758.4	756.9	755.4	756.9	758.4	759.9	761.4	762.2
177.5°	763.3	762.5	761.0	759.5	758.0	756.5	758.0	759.5	761.0	762.5	763.3
180°	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9	929.9
2.5°	874.4	879.1	874.4	877.5	879.1	882.9	884.4	891.4	893.7	899.1	899.1
5°	822.0	824.4	825.1	828.2	831.3	839.0	844.4	854.4	866.0	867.5	874.4
7.5°	779.7	783.5	789.7	787.4	792.8	804.3	811.3	823.6	835.1	841.3	849.8
10°	741.9	746.5	748.9	751.2	761.2	771.2	782.0	790.5	805.9	815.1	822.0
12.5°	711.1	707.3	711.9	720.3	731.9	738.1	752.7	765.8	777.4	787.4	793.5
15°	671.0	674.1	678.7	693.4	696.5	711.9	717.3	731.9	753.5	762.7	770.4
17.5°	632.5	642.5	651.8	657.2	666.4	678.7	694.2	710.3	724.2	735.0	744.2
20°	601.7	611.7	617.1	621.0	630.2	647.2	661.8	681.8	699.5	708.0	720.3
22.5°	577.0	577.0	584.8	596.3	601.7	617.9	630.2	651.8	671.0	681.8	693.4
25°	546.2	550.9	557.0	567.0	574.7	587.8	605.6	624.0	644.8	654.1	668.7
27.5°	520.8	526.2	534.7	537.0	544.7	556.2	574.7	594.8	616.3	626.4	638.7
30°	501.5	504.6	507.7	512.3	519.3	529.3	544.7	562.4	588.6	596.3	611.7
32.5°	484.6	486.1	487.7	491.5	495.4	505.4	517.7	537.0	558.6	570.1	584.0
35°	469.2	467.6	468.4	470.7	474.6	478.4	491.5	507.7	527.7	541.6	552.4
37.5°	454.6	451.5	450.7	450.7	452.2	456.9	466.9	480.7	502.3	513.9	524.7
40°	438.4	435.3	433.7	433.0	432.2	435.3	443.0	456.9	473.8	484.6	496.9
42.5°	423.0	419.9	416.0	415.3	413.7	415.3	420.7	433.7	448.4	459.2	469.2
45°	407.6	402.2	397.5	394.5	395.2	392.9	396.8	406.8	423.7	430.7	440.7
47.5°	390.6	384.4	378.3	375.2	372.1	373.7	375.2	383.7	398.3	405.2	415.3
50°	374.4	366.0	359.0	355.2	352.9	351.3	352.9	361.3	372.1	378.3	386.8
52.5°	355.9	347.5	340.5	334.4	331.3	329.0	329.7	337.4	347.5	353.6	362.1
55°	339.0	328.2	319.0	311.3	308.9	308.2	307.4	312.8	321.3	327.4	334.4
57.5°	319.7	308.9	298.9	289.7	285.1	284.3	284.3	285.8	296.6	301.2	305.1
60°	300.5	288.9	278.1	269.6	262.7	260.4	259.6	262.7	268.1	272.7	278.1
62.5°	278.9	267.3	254.2	246.5	239.6	233.4	235.8	236.5	244.2	246.5	251.2
65°	258.1	245.0	234.2	221.9	214.2	210.3	208.8	210.3	216.5	217.3	220.3
67.5°	234.2	221.9	208.8	200.3	193.4	186.4	184.9	184.9	188.0	190.3	194.1
70°	211.1	198.8	184.1	174.9	168.0	161.8	159.5	158.7	161.0	162.6	166.4
72.5°	184.1	171.8	161.0	151.0	142.5	137.9	135.6	134.1	136.4	137.9	138.7
75°	155.6	145.6	134.8	124.8	119.4	114.8	111.7	109.4	110.9	110.9	110.9
77.5°	128.7	118.6	110.2	103.2	96.3	90.9	88.6	86.3	87.1	87.1	88.6
80°	100.2	93.2	86.3	80.1	74.0	69.3	67.8	65.5	63.9	63.2	63.2
82.5°	74.0	68.6	62.4	57.0	53.9	49.3	47.8	44.7	44.7	43.9	43.9
85°	49.3	46.2	40.1	36.2	33.9	31.6	30.0	28.5	26.2	26.2	25.4
87.5°	26.2	24.7	23.1	18.5	18.5	16.2	15.4	14.6	12.3	13.1	13.1
90°	15.5	14.8	14.0	13.3	12.5	11.5	10.5	9.5	8.5	8.0	7.3
92.5°	14.9	14.2	13.4	12.7	11.9	10.9	9.9	8.9	7.9	7.4	7.5
95°	15.5	14.8	14.0	13.3	12.5	12.4	12.2	12.1	12.0	11.9	14.1
97.5°	15.0	14.4	13.7	13.1	12.5	25.8	39.0	52.3	65.6	72.2	70.8
100°	16.4	18.5	20.7	22.8	25.0	42.4	59.8	77.3	94.7	103.4	102.3
102.5°	30.7	59.1	87.6	116.0	144.4	142.9	141.3	139.8	138.3	137.5	136.7
105°	181.8	180.7	179.6	178.4	177.3	176.7	176.1	175.4	174.8	174.5	174.1
107.5°	216.2	215.6	214.9	214.3	213.7	212.8	211.9	211.0	210.1	209.7	209.5
110°	251.7	251.4	251.2	250.9	250.7	249.9	249.1	248.4	247.6	247.2	247.0

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	286.0	286.1	286.2	286.4	286.5	286.2	286.0	285.7	285.4	285.3	284.9
115°	321.6	321.3	321.1	320.8	320.6	320.7	320.8	320.9	321.0	321.1	320.9
117.5°	356.5	356.6	356.7	356.8	356.9	356.5	356.1	355.8	355.4	355.2	355.0
120°	389.8	389.5	389.3	389.0	388.8	388.9	389.0	389.1	389.2	389.3	389.1
122.5°	421.6	421.5	421.4	421.3	421.2	420.9	420.7	420.4	420.1	420.0	419.9
125°	451.7	451.3	450.9	450.5	450.1	450.4	450.6	450.9	451.2	451.3	451.0
127.5°	480.9	481.0	481.1	481.3	481.4	480.8	480.2	479.5	478.9	478.6	478.5
130°	508.6	508.5	508.4	508.2	508.1	507.7	507.3	507.0	506.6	506.4	506.3
132.5°	535.3	535.2	535.1	534.9	534.8	534.3	533.8	533.3	532.8	532.6	532.5
135°	559.7	559.4	559.2	558.9	558.7	558.2	557.7	557.2	556.7	556.4	556.5
137.5°	583.6	583.3	583.1	582.8	582.6	582.0	581.3	580.7	580.0	579.7	579.7
140°	605.7	605.3	605.0	604.6	604.2	603.9	603.7	603.4	603.1	603.0	602.9
142.5°	625.7	625.4	625.1	624.9	624.6	624.5	624.4	624.3	624.2	624.1	623.8
145°	644.4	644.3	644.2	644.1	644.0	644.0	644.0	644.0	644.0	644.0	643.8
147.5°	661.5	661.4	661.3	661.1	661.0	661.1	661.3	661.4	661.5	661.6	661.2
150°	677.5	677.5	677.5	677.5	677.5	677.6	677.8	677.9	678.0	678.1	677.8
152.5°	692.2	691.9	691.6	691.4	691.1	691.4	691.6	691.9	692.2	692.3	692.1
155°	705.1	704.6	704.1	703.6	703.1	703.5	703.9	704.2	704.6	704.8	704.7
157.5°	716.4	715.8	715.1	714.5	713.9	714.4	714.9	715.4	715.9	716.1	716.1
160°	727.1	726.4	725.6	724.9	724.1	724.2	724.4	724.5	724.6	724.7	724.9
162.5°	735.6	734.9	734.1	733.4	732.6	732.7	732.9	733.0	733.1	733.2	733.5
165°	744.1	743.1	742.0	741.0	740.0	740.0	740.0	740.0	740.0	740.0	740.3
167.5°	750.2	749.1	748.0	746.8	745.7	745.8	746.0	746.1	746.2	746.3	746.6
170°	755.4	754.4	753.4	752.4	751.4	751.3	751.1	751.0	750.9	750.8	751.2
172.5°	758.8	757.8	756.8	755.8	754.8	754.7	754.5	754.4	754.3	754.2	754.6
175°	761.6	760.5	759.4	758.2	757.1	757.0	756.8	756.7	756.6	756.5	756.9
177.5°	762.8	761.8	760.8	759.8	758.8	758.5	758.3	758.0	757.7	757.6	758.0
180°	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9	759.9

TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	929.9	929.9	929.9	929.9
2.5°	904.5	912.2	919.1	929.9
5°	884.4	895.2	909.9	926.1
7.5°	861.3	878.3	897.5	919.9
10°	839.8	859.0	883.7	910.6
12.5°	817.4	840.5	867.5	896.8
15°	792.0	815.1	845.2	884.4
17.5°	768.9	796.6	829.0	870.6
20°	741.9	768.1	803.6	851.3
22.5°	718.0	748.1	787.4	829.0
25°	691.8	718.0	757.3	807.4
27.5°	665.6	698.0	735.8	784.3
30°	640.2	667.2	708.0	758.9
32.5°	612.5	644.8	682.6	730.4
35°	582.4	613.3	648.7	700.3
37.5°	555.5	585.5	621.7	667.2
40°	525.4	557.0	590.1	635.6
42.5°	496.2	524.7	557.8	599.4
45°	467.6	492.3	522.3	558.6
47.5°	438.4	459.2	486.9	519.3
50°	406.8	429.1	449.9	476.9
52.5°	377.5	396.8	413.7	436.1
55°	349.0	362.1	376.0	392.9
57.5°	319.0	329.0	339.0	356.7
60°	288.9	298.2	303.5	315.1
62.5°	259.6	263.5	270.4	277.4
65°	227.3	232.7	236.5	245.0
67.5°	198.0	200.3	204.2	209.6
70°	167.2	172.6	174.1	178.0
72.5°	141.0	143.3	144.8	145.6
75°	111.7	114.0	115.6	120.2
77.5°	87.8	87.1	90.1	90.9
80°	64.7	62.4	63.2	66.3
82.5°	42.4	43.1	42.4	42.4
85°	26.2	25.4	23.9	24.7
87.5°	11.6	11.6	10.8	10.8
90°	5.9	4.5	3.1	1.7
92.5°	7.8	8.0	8.3	8.5
95°	18.4	22.7	27.0	31.3
97.5°	68.0	65.3	62.5	59.7
100°	100.0	97.7	95.5	93.2
102.5°	135.2	133.7	132.2	130.7
105°	173.4	172.6	171.9	171.1
107.5°	209.1	208.8	208.4	208.0
110°	246.6	246.3	245.9	245.5



TEST NUMBER: P1025641

CATALOG NUMBER: S124DIP-B575D590UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	284.2	283.4	282.7	281.9
115°	320.5	320.2	319.8	319.4
117.5°	354.5	354.0	353.5	353.0
120°	388.6	388.1	387.6	387.1
122.5°	419.6	419.4	419.1	418.9
125°	450.5	450.0	449.5	449.0
127.5°	478.4	478.3	478.1	478.0
130°	506.2	506.1	505.9	505.8
132.5°	532.2	531.9	531.7	531.4
135°	556.6	556.7	556.9	557.0
137.5°	579.7	579.7	579.7	579.7
140°	602.6	602.4	602.1	601.9
142.5°	623.3	622.8	622.3	621.8
145°	643.4	643.1	642.7	642.3
147.5°	660.5	659.7	659.0	658.2
150°	677.3	676.8	676.3	675.8
152.5°	691.7	691.4	691.0	690.6
155°	704.6	704.5	704.3	704.2
157.5°	716.1	716.1	716.1	716.1
160°	725.3	725.6	726.0	726.4
162.5°	734.0	734.5	735.0	735.5
165°	741.0	741.6	742.3	742.9
167.5°	747.2	747.9	748.5	749.1
170°	751.9	752.7	753.4	754.2
172.5°	755.3	756.1	756.8	757.6
175°	757.6	758.4	759.1	759.9
177.5°	758.9	759.8	760.7	761.6
180°	759.9	759.9	759.9	759.9

(END OF REPORT)