

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025967

Luminaire Tested: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025967
REPORT IS A COMBINATION OF REPORTS P998877 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8618.0 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	50
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	50	49	48	48	48	43
2	90	83	77	72	83	77	72	67	65	61	58	55	52	50	45	43	41	41	41	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	36	36	32
4	75	65	57	51	69	60	54	48	52	47	42	44	40	37	36	33	31	31	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	27	27	24
6	64	52	44	39	59	49	42	36	42	36	32	36	31	28	30	27	24	24	24	21
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	27	24	22	22	22	19
8	55	43	35	30	51	40	33	29	35	29	26	30	26	22	25	22	20	20	20	17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	18	18	16
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	22	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13907	13907	13907	13907
5°	13906	15714	13929	12010
10°	13833	18114	13821	10445
15°	13667	20387	13667	8745
20°	13495	22104	13425	7701
25°	13286	22198	13224	6955
30°	13062	18876	12960	6442
35°	12745	14242	12584	6060
40°	12394	10322	12150	5762
45°	11812	7845	11519	5497
50°	11122	6340	10817	5110
55°	10375	5250	10036	4595
60°	9623	4439	9195	3821
65°	8682	3616	8406	3037
70°	7817	2933	7449	2467
75°	6850	2113	6374	1808
80°	5651	1401	5145	1330
85°	4097	721	3398	721

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 17409 cd/sqm

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.1	1.9
10°-20°	498.7	5.8
20°-30°	781.1	9.1
30°-40°	867.4	10.1
40°-50°	768.7	8.9
50°-60°	599.0	7.0
60°-70°	391.8	4.5
70°-80°	192.3	2.2
80°-90°	49.1	0.6
90°-100°	428.4	5.0
100°-110°	894.3	10.4
110°-120°	795.0	9.2
120°-130°	669.2	7.8
130°-140°	558.3	6.5
140°-150°	426.3	4.9
150°-160°	299.7	3.5
160°-170°	176.3	2.0
170°-180°	57.3	0.7
0°-30°	1445.0	16.8
0°-40°	2312.4	26.8
0°-60°	3680.1	42.7
0°-90°	4313.3	50.1
90°-120°	2117.6	24.6
90°-150°	3771.4	43.8
90°-180°	4305.0	50.0
0°-180°	8618.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1705	1705	1705	1705	1705	
5°	1703	1971	1705	1506	1703	162
15°	1630	2611	1630	1120	1630	460
25°	1494	2816	1487	882	1494	688
35°	1303	1734	1286	738	1303	814
45°	1050	886	1024	621	1050	810
55°	756	529	731	463	756	676
65°	474	309	459	260	474	473
75°	238	143	221	122	238	252
85°	56	34	47	34	56	64
90°	1	24	1	24	1	6
95°	38	283	38	283	38	42
105°	136	1634	136	1634	136	145
115°	239	1569	239	1569	239	237
125°	333	1252	333	1252	333	297
135°	396	1119	396	1119	396	306
145°	456	914	456	914	456	286
155°	519	765	519	765	519	239
165°	566	668	566	668	566	160
175°	590	602	590	602	590	56
180°	591	591	591	591	591	

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1708.1	1723.2	1731.5	1738.4	1752.1	1757.6	1768.6	1771.3	1782.3	1781.0	1776.8
5°	1702.6	1728.7	1748.0	1768.6	1793.3	1807.1	1822.2	1844.2	1855.2	1870.3	1879.9
7.5°	1693.0	1728.7	1760.3	1792.0	1831.8	1853.8	1873.0	1907.4	1936.2	1961.0	1988.5
10°	1677.9	1723.2	1770.0	1812.6	1867.5	1893.6	1922.5	1973.3	2013.2	2047.6	2091.5
12.5°	1654.5	1717.7	1770.0	1827.7	1897.8	1933.5	1972.0	2032.4	2079.2	2135.5	2190.5
15°	1629.8	1699.9	1768.6	1844.2	1923.9	1965.1	2003.6	2084.7	2156.1	2220.7	2281.2
17.5°	1602.3	1679.3	1754.9	1838.7	1934.9	1985.7	2031.1	2128.6	2207.0	2290.8	2351.3
20°	1569.3	1653.2	1739.7	1833.2	1941.7	1998.1	2048.9	2160.2	2246.8	2337.5	2413.1
22.5°	1533.6	1624.3	1719.1	1820.8	1933.5	1995.3	2054.4	2174.0	2274.3	2358.1	2459.8
25°	1493.8	1589.9	1687.5	1794.7	1921.1	1988.5	2048.9	2167.1	2274.3	2384.2	2483.2
27.5°	1452.5	1551.5	1653.2	1765.8	1895.0	1961.0	2029.7	2143.7	2268.8	2388.4	2488.7
30°	1407.2	1503.4	1610.6	1717.7	1855.2	1921.1	1991.2	2114.9	2250.9	2370.5	2479.1
32.5°	1357.7	1456.6	1558.3	1669.7	1804.3	1875.8	1940.4	2080.5	2219.3	2337.5	2439.2
35°	1302.7	1396.2	1492.4	1606.4	1739.7	1804.3	1881.3	2026.9	2167.1	2292.2	2358.1
37.5°	1243.6	1333.0	1422.3	1535.0	1662.8	1741.1	1816.7	1963.7	2112.1	2196.0	2230.3
40°	1188.7	1267.0	1345.3	1453.9	1583.1	1664.2	1741.1	1893.6	2024.2	2088.8	2062.7
42.5°	1118.6	1199.7	1269.8	1370.1	1500.6	1576.2	1654.5	1812.6	1918.4	1944.5	1879.9
45°	1049.9	1117.2	1184.6	1282.1	1419.5	1484.1	1568.0	1715.0	1802.9	1779.6	1684.8
47.5°	982.6	1037.5	1100.7	1195.6	1319.2	1396.2	1474.5	1602.3	1664.2	1631.2	1499.3
50°	902.8	957.8	1023.8	1106.2	1225.8	1300.0	1361.8	1480.0	1526.7	1445.7	1286.2
52.5°	827.3	875.4	931.7	1008.7	1122.7	1190.1	1257.4	1359.1	1374.2	1280.8	1113.1
55°	755.8	794.3	853.4	915.2	1019.7	1091.1	1137.8	1224.4	1220.3	1103.5	959.2
57.5°	681.6	717.3	757.2	821.8	920.7	974.3	1025.2	1100.7	1060.9	961.9	819.0
60°	615.6	636.3	676.1	737.9	821.8	868.5	908.3	949.6	915.2	808.0	698.1
62.5°	542.8	566.2	595.0	644.5	718.7	762.7	791.5	809.4	773.7	691.2	590.9
65°	474.1	494.7	524.9	568.9	625.3	658.2	673.4	685.7	666.5	573.0	493.3
67.5°	412.3	426.0	453.5	482.3	542.8	551.1	571.7	577.2	538.7	467.2	404.0
70°	350.4	364.2	376.5	410.9	438.4	453.5	457.6	457.6	419.1	372.4	320.2
72.5°	292.7	300.9	313.3	336.7	351.8	362.8	368.3	361.4	325.7	287.2	248.7
75°	237.7	241.9	252.9	268.0	280.3	276.2	274.8	266.6	240.5	213.0	191.0
77.5°	182.8	185.5	197.9	202.0	202.0	206.1	200.6	192.4	170.4	149.8	140.2
80°	137.4	141.5	142.9	145.7	142.9	142.9	138.8	125.1	114.1	104.4	97.6
82.5°	94.8	97.6	98.9	94.8	97.6	93.4	86.6	77.0	70.1	68.7	66.0
85°	56.3	57.7	56.3	56.3	52.2	50.8	45.3	44.0	41.2	41.2	39.9
87.5°	27.5	26.1	23.4	20.6	20.6	19.2	20.6	17.9	20.6	19.2	17.9
90°	1.2	3.5	7.0	8.1	9.3	9.3	9.3	16.3	16.3	18.6	20.9
92.5°	16.3	23.2	36.0	53.4	74.3	89.4	104.5	176.5	289.1	398.3	455.2
95°	38.3	41.8	53.4	68.5	96.4	120.8	145.1	246.2	436.6	714.1	946.4
97.5°	63.9	63.9	74.3	88.2	112.6	133.5	154.4	234.6	398.3	683.9	1012.5
100°	88.2	88.2	96.4	110.3	132.4	151.0	169.5	238.0	369.3	606.1	933.6
102.5°	111.5	113.8	120.8	133.5	154.4	171.9	189.3	249.7	361.1	553.9	834.9
105°	135.9	139.3	145.1	159.1	180.0	196.8	213.7	269.4	365.8	528.3	761.7
107.5°	162.6	164.9	170.7	185.8	205.5	222.4	239.2	290.3	379.7	521.4	714.1
110°	189.3	191.6	197.4	211.3	232.2	247.9	263.6	314.7	396.0	523.7	692.1



TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	214.8	217.1	224.1	236.9	257.8	273.5	289.1	337.9	413.4	530.7	681.6
115°	239.2	242.7	250.8	262.4	284.5	300.2	315.8	362.3	432.0	539.9	679.3
117.5°	264.7	268.2	275.2	288.0	308.9	325.2	341.4	385.5	450.5	549.2	678.1
120°	290.3	292.6	300.7	313.5	333.3	349.6	365.8	409.9	470.3	559.7	678.1
122.5°	313.5	315.8	324.0	335.6	357.6	373.3	389.0	433.1	488.9	570.1	677.0
125°	333.3	337.9	344.9	357.6	379.7	396.0	412.2	454.0	507.4	580.6	675.8
127.5°	351.8	355.3	363.4	377.4	400.6	416.8	433.1	473.8	523.7	588.7	673.5
130°	366.9	371.6	380.9	398.3	420.3	437.2	454.0	493.5	538.8	598.0	672.3
132.5°	382.0	385.5	398.3	414.5	438.9	454.6	470.3	509.8	553.9	606.1	671.2
135°	396.0	400.6	412.2	432.0	456.3	471.4	486.5	524.9	566.7	614.3	670.0
137.5°	409.9	414.5	427.3	445.9	471.4	486.0	500.5	536.5	575.9	618.9	670.0
140°	425.0	428.5	441.2	461.0	485.4	499.3	513.2	548.1	585.2	624.7	668.8
142.5°	441.2	444.7	456.3	474.9	498.1	511.5	524.9	558.5	592.2	629.4	668.8
145°	456.3	459.8	471.4	487.7	509.8	522.6	535.3	565.5	596.8	630.5	666.5
147.5°	473.8	474.9	485.4	502.8	521.4	533.0	544.6	573.6	601.5	631.7	663.0
150°	490.0	491.2	500.5	514.4	531.8	542.8	553.9	579.4	605.0	631.7	659.5
152.5°	505.1	505.1	514.4	527.2	542.3	552.2	562.0	584.1	607.3	629.4	653.7
155°	519.0	520.2	527.2	538.8	551.6	560.3	569.0	588.7	608.5	627.0	647.9
157.5°	533.0	533.0	539.9	549.2	560.8	567.8	574.8	592.2	608.5	624.7	642.1
160°	545.8	545.8	550.4	558.5	567.8	574.2	580.6	594.5	608.5	621.2	635.2
162.5°	557.4	556.2	559.7	566.7	574.8	579.4	584.1	596.8	608.5	617.7	628.2
165°	565.5	565.5	567.8	573.6	579.4	582.9	586.4	596.8	606.1	613.1	621.2
167.5°	574.8	573.6	574.8	579.4	582.9	585.8	588.7	596.8	603.8	608.5	614.3
170°	580.6	579.4	580.6	584.1	586.4	588.2	589.9	595.7	601.5	603.8	607.3
172.5°	586.4	585.2	585.2	587.6	588.7	589.8	591.0	594.5	599.2	599.2	600.3
175°	589.9	588.7	588.7	589.9	591.0	591.0	591.0	593.4	596.8	595.7	595.7
177.5°	592.2	591.0	589.9	591.0	591.0	591.0	591.0	592.2	594.5	592.2	592.2
180°	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1787.8	1802.9	1804.3	1818.1	1813.9	1807.1	1819.4	1811.2	1827.7	1822.2	1829.1
5°	1892.3	1912.9	1930.7	1941.7	1961.0	1956.9	1977.5	1970.6	1985.7	1970.6	1989.8
7.5°	2014.6	2048.9	2066.8	2095.7	2103.9	2105.3	2130.0	2135.5	2145.1	2135.5	2146.5
10°	2134.1	2175.4	2216.6	2239.9	2255.1	2275.7	2297.7	2307.3	2314.1	2304.5	2311.4
12.5°	2242.7	2307.3	2352.6	2399.3	2410.3	2428.2	2451.6	2448.8	2476.3	2470.8	2483.2
15°	2343.0	2414.5	2469.4	2506.5	2536.8	2551.9	2595.9	2598.6	2597.2	2611.0	2602.7
17.5°	2432.3	2492.8	2571.1	2619.2	2656.3	2656.3	2681.1	2731.9	2727.8	2726.4	2734.7
20°	2505.2	2573.9	2646.7	2727.8	2758.0	2763.5	2797.9	2824.0	2828.1	2828.1	2828.1
22.5°	2560.1	2641.2	2719.5	2777.3	2800.6	2819.9	2850.1	2866.6	2872.1	2869.3	2872.1
25°	2587.6	2664.6	2744.3	2796.5	2810.2	2821.2	2824.0	2833.6	2832.2	2815.7	2825.4
27.5°	2593.1	2667.3	2719.5	2733.3	2726.4	2719.5	2675.6	2679.7	2667.3	2642.6	2652.2
30°	2568.4	2608.2	2606.9	2564.3	2551.9	2523.0	2483.2	2424.1	2376.0	2355.4	2362.2
32.5°	2479.1	2479.1	2429.6	2333.4	2290.8	2238.6	2167.1	2113.5	2050.3	2036.6	2062.7
35°	2355.4	2285.3	2194.6	2068.2	2003.6	1965.1	1841.4	1802.9	1749.4	1734.2	1746.6
37.5°	2163.0	2046.2	1914.3	1796.1	1741.1	1672.4	1563.8	1508.9	1470.4	1444.3	1456.6
40°	1947.2	1805.7	1668.3	1522.6	1462.1	1405.8	1324.7	1275.3	1213.4	1216.2	1220.3
42.5°	1741.1	1574.8	1420.9	1286.2	1228.5	1181.8	1125.5	1065.0	1043.0	1036.1	1029.3
45°	1522.6	1345.3	1201.0	1100.7	1048.5	1004.5	952.3	918.0	891.9	886.4	893.2
47.5°	1316.5	1166.7	1029.3	935.8	893.2	871.2	830.0	798.4	781.9	768.2	776.4
50°	1129.6	989.4	879.5	801.2	770.9	755.8	717.3	700.8	684.4	680.2	678.9
52.5°	975.7	856.1	761.3	698.1	674.7	666.5	637.6	614.3	600.5	604.6	607.4
55°	835.5	733.8	659.6	608.8	589.5	579.9	559.3	542.8	533.2	529.1	531.8
57.5°	711.8	623.9	570.3	529.1	514.0	509.8	487.8	482.3	475.5	471.3	471.3
60°	599.2	537.3	487.8	464.5	448.0	443.9	427.4	420.5	419.1	415.0	412.3
62.5°	504.3	453.5	419.1	394.4	387.5	386.1	375.2	366.9	362.8	360.0	360.0
65°	421.9	384.8	355.9	338.1	332.6	329.8	317.4	314.7	311.9	309.2	307.8
67.5°	351.8	318.8	298.2	285.8	279.0	280.3	273.5	268.0	268.0	266.6	265.2
70°	284.5	263.8	246.0	239.1	236.4	233.6	230.9	226.7	225.4	225.4	225.4
72.5°	224.0	210.3	200.6	196.5	193.8	191.0	188.3	188.3	188.3	186.9	186.9
75°	171.8	166.3	159.4	155.3	155.3	158.0	153.9	149.8	145.7	142.9	144.3
77.5°	129.2	126.4	122.3	115.4	116.8	114.1	114.1	111.3	112.7	112.7	109.9
80°	94.8	90.7	89.3	85.2	86.6	85.2	83.8	83.8	81.1	81.1	81.1
82.5°	66.0	61.8	61.8	60.5	59.1	59.1	57.7	57.7	59.1	56.3	56.3
85°	39.9	38.5	38.5	35.7	35.7	35.7	35.7	37.1	35.7	34.4	34.4
87.5°	17.9	19.2	17.9	16.5	16.5	16.5	15.1	15.1	13.7	15.1	15.1
90°	19.7	20.9	22.1	23.2	23.2	23.2	24.4	25.5	24.4	24.4	24.4
92.5°	378.5	279.8	209.0	164.9	150.4	135.9	118.4	110.3	105.7	105.7	105.7
95°	973.1	860.4	680.4	524.9	468.6	412.2	355.3	319.3	298.4	283.3	298.4
97.5°	1220.4	1239.0	1149.6	1021.8	956.8	891.8	812.8	743.2	708.3	680.4	708.3
100°	1230.8	1400.4	1423.6	1366.7	1323.8	1280.8	1179.8	1108.9	1074.1	1064.8	1074.1
102.5°	1143.8	1392.2	1530.4	1565.3	1553.6	1542.0	1489.8	1443.3	1406.2	1399.2	1406.2
105°	1034.6	1300.5	1501.4	1616.4	1640.2	1664.0	1666.3	1657.0	1640.7	1633.8	1640.7
107.5°	945.2	1187.9	1405.0	1565.3	1614.0	1662.8	1713.9	1734.8	1744.1	1745.2	1744.1
110°	881.3	1088.0	1288.9	1457.3	1521.2	1585.0	1667.4	1716.2	1737.1	1747.6	1737.1

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	845.3	1014.9	1186.7	1343.5	1407.4	1471.2	1567.6	1629.1	1660.5	1679.1	1660.5
115°	825.6	970.7	1113.6	1249.4	1305.2	1360.9	1452.6	1522.3	1559.5	1568.7	1559.5
117.5°	815.1	945.2	1066.0	1176.3	1225.0	1273.8	1355.1	1415.5	1455.0	1460.8	1455.0
120°	807.0	928.9	1036.9	1129.8	1171.0	1212.3	1278.5	1329.5	1359.7	1372.5	1359.7
122.5°	797.7	915.0	1018.3	1100.8	1135.6	1170.5	1223.9	1265.7	1290.1	1302.8	1290.1
125°	787.3	898.7	998.6	1078.7	1110.6	1142.6	1189.0	1222.7	1244.8	1251.7	1244.8
127.5°	773.3	880.2	976.5	1056.7	1086.8	1117.0	1163.5	1193.7	1212.3	1219.2	1212.3
130°	760.6	856.9	948.7	1027.6	1058.4	1089.2	1136.8	1165.8	1184.4	1191.4	1184.4
132.5°	749.0	832.6	917.3	994.0	1024.8	1055.5	1102.0	1135.6	1153.0	1160.0	1153.0
135°	737.3	810.5	886.0	956.8	985.8	1014.9	1061.3	1093.8	1112.4	1119.4	1112.4
137.5°	726.9	789.6	855.8	917.3	944.0	970.7	1014.9	1048.5	1063.6	1071.8	1063.6
140°	718.8	772.2	826.8	879.0	903.4	927.8	968.4	994.0	1010.2	1019.5	1010.2
142.5°	711.8	755.9	802.4	845.3	865.6	886.0	920.8	944.0	958.0	963.8	958.0
145°	703.7	740.8	780.3	815.1	831.4	847.7	876.7	896.4	908.0	913.8	908.0
147.5°	696.7	728.1	760.6	789.6	803.0	816.3	838.4	855.8	865.1	867.4	865.1
150°	688.6	716.4	743.2	766.4	776.8	787.3	805.9	820.9	827.9	829.1	827.9
152.5°	679.3	703.7	725.7	746.6	754.8	762.9	778.0	789.6	793.1	794.2	793.1
155°	670.0	690.9	709.5	726.9	733.8	740.8	752.4	761.7	765.2	765.2	765.2
157.5°	660.7	677.0	693.2	708.3	714.1	719.9	729.2	736.2	738.5	738.5	738.5
160°	650.3	664.2	677.0	689.7	694.4	699.0	706.0	713.0	714.1	714.1	714.1
162.5°	641.0	651.4	661.9	671.2	675.2	679.3	683.9	690.9	692.1	690.9	692.1
165°	630.5	639.8	646.8	654.9	657.8	660.7	665.4	670.0	668.8	667.7	668.8
167.5°	621.2	628.2	634.0	641.0	642.8	644.5	646.8	650.3	650.3	649.1	650.3
170°	611.9	617.7	621.2	625.9	627.6	629.4	631.7	632.8	631.7	631.7	631.7
172.5°	603.8	608.5	610.8	613.1	614.2	615.4	616.6	617.7	616.6	614.3	616.6
175°	598.0	600.3	601.5	603.8	603.8	603.8	603.8	606.1	603.8	601.5	603.8
177.5°	593.4	594.5	595.7	595.7	596.2	596.8	595.7	596.8	594.5	592.2	594.5
180°	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1833.2	1823.6	1822.2	1822.2	1807.1	1815.3	1798.8	1781.0	1772.7	1772.7	1757.6
5°	1985.7	1976.1	1966.5	1951.4	1951.4	1943.1	1917.0	1890.9	1871.7	1855.2	1837.3
7.5°	2142.4	2132.8	2105.3	2090.2	2098.4	2081.9	2047.6	2003.6	1970.6	1944.5	1907.4
10°	2312.8	2286.7	2272.9	2264.7	2235.8	2218.0	2178.1	2113.5	2072.3	2037.9	1989.8
12.5°	2451.6	2459.8	2407.6	2411.7	2382.9	2358.1	2296.3	2234.4	2172.6	2124.5	2053.1
15°	2601.4	2576.6	2545.0	2520.3	2510.7	2480.4	2428.2	2345.8	2278.4	2202.8	2121.8
17.5°	2719.5	2700.3	2670.1	2646.7	2626.1	2553.3	2509.3	2436.5	2344.4	2270.2	2171.2
20°	2819.9	2802.0	2759.4	2744.3	2707.2	2655.0	2591.7	2479.1	2396.6	2315.5	2219.3
22.5°	2862.5	2844.6	2807.5	2788.2	2764.9	2714.0	2653.6	2546.4	2444.7	2343.0	2241.3
25°	2826.7	2826.7	2808.9	2802.0	2781.4	2736.0	2674.2	2583.5	2474.9	2365.0	2244.1
27.5°	2653.6	2687.9	2700.3	2707.2	2707.2	2708.5	2665.9	2578.0	2472.2	2365.0	2238.6
30°	2403.5	2461.2	2512.0	2527.2	2553.3	2582.1	2600.0	2557.4	2462.6	2349.9	2223.5
32.5°	2088.8	2163.0	2257.8	2281.2	2316.9	2403.5	2451.6	2469.4	2417.2	2318.3	2183.6
35°	1775.5	1868.9	1926.6	1998.1	2031.1	2158.9	2266.1	2330.6	2318.3	2259.2	2136.9
37.5°	1502.0	1555.6	1625.7	1701.3	1767.2	1889.5	2022.8	2147.9	2198.7	2169.9	2077.8
40°	1239.5	1302.7	1386.6	1448.4	1493.8	1616.1	1781.0	1917.0	2028.3	2046.2	1989.8
42.5°	1054.0	1117.2	1168.1	1235.4	1271.1	1389.3	1535.0	1705.4	1837.3	1907.4	1882.7
45°	911.1	949.6	990.8	1029.3	1073.2	1177.7	1312.4	1499.3	1647.7	1746.6	1756.2
47.5°	786.0	820.4	856.1	891.9	916.6	997.7	1121.3	1273.9	1436.0	1572.1	1625.7
50°	698.1	714.6	740.7	761.3	790.2	860.2	959.2	1091.1	1262.9	1409.9	1480.0
52.5°	611.5	632.1	652.7	670.6	689.8	739.3	830.0	944.1	1092.5	1243.6	1330.2
55°	538.7	555.2	574.4	586.8	597.8	641.8	710.5	798.4	926.2	1069.1	1176.3
57.5°	479.6	486.5	503.0	509.8	522.2	557.9	607.4	685.7	788.8	927.6	1015.5
60°	415.0	428.7	441.1	446.6	456.2	481.0	515.3	588.2	677.5	779.2	879.5
62.5°	362.8	368.3	377.9	384.8	391.6	417.8	446.6	501.6	568.9	654.1	746.2
65°	314.7	317.4	322.9	332.6	336.7	355.9	372.4	412.3	475.5	540.1	632.1
67.5°	265.2	268.0	274.8	280.3	284.5	296.8	314.7	343.5	377.9	449.4	500.2
70°	226.7	226.7	230.9	233.6	237.7	243.2	252.9	274.8	306.4	351.8	398.5
72.5°	189.6	189.6	189.6	193.8	193.8	197.9	203.4	218.5	240.5	276.2	306.4
75°	147.0	148.4	151.2	151.2	152.5	158.0	162.2	166.3	177.3	200.6	228.1
77.5°	111.3	114.1	115.4	112.7	115.4	115.4	120.9	126.4	131.9	138.8	159.4
80°	82.5	83.8	81.1	82.5	82.5	85.2	87.9	86.6	89.3	97.6	103.1
82.5°	55.0	56.3	56.3	56.3	56.3	60.5	60.5	59.1	60.5	61.8	63.2
85°	34.4	33.0	33.0	34.4	33.0	33.0	34.4	35.7	34.4	35.7	37.1
87.5°	15.1	15.1	15.1	15.1	13.7	13.7	15.1	13.7	15.1	13.7	12.4
90°	25.5	24.4	23.2	23.2	23.2	22.1	20.9	19.7	20.9	18.6	16.3
92.5°	110.3	118.4	135.9	150.4	164.9	209.0	279.8	378.5	455.2	398.3	289.1
95°	319.3	355.3	412.2	468.6	524.9	680.4	860.4	973.1	946.4	714.1	436.6
97.5°	743.2	812.8	891.8	956.8	1021.8	1149.6	1239.0	1220.4	1012.5	683.9	398.3
100°	1108.9	1179.8	1280.8	1323.8	1366.7	1423.6	1400.4	1230.8	933.6	606.1	369.3
102.5°	1443.3	1489.8	1542.0	1553.6	1565.3	1530.4	1392.2	1143.8	834.9	553.9	361.1
105°	1657.0	1666.3	1664.0	1640.2	1616.4	1501.4	1300.5	1034.6	761.7	528.3	365.8
107.5°	1734.8	1713.9	1662.8	1614.0	1565.3	1405.0	1187.9	945.2	714.1	521.4	379.7
110°	1716.2	1667.4	1585.0	1521.2	1457.3	1288.9	1088.0	881.3	692.1	523.7	396.0

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1629.1	1567.6	1471.2	1407.4	1343.5	1186.7	1014.9	845.3	681.6	530.7	413.4
115°	1522.3	1452.6	1360.9	1305.2	1249.4	1113.6	970.7	825.6	679.3	539.9	432.0
117.5°	1415.5	1355.1	1273.8	1225.0	1176.3	1066.0	945.2	815.1	678.1	549.2	450.5
120°	1329.5	1278.5	1212.3	1171.0	1129.8	1036.9	928.9	807.0	678.1	559.7	470.3
122.5°	1265.7	1223.9	1170.5	1135.6	1100.8	1018.3	915.0	797.7	677.0	570.1	488.9
125°	1222.7	1189.0	1142.6	1110.6	1078.7	998.6	898.7	787.3	675.8	580.6	507.4
127.5°	1193.7	1163.5	1117.0	1086.8	1056.7	976.5	880.2	773.3	673.5	588.7	523.7
130°	1165.8	1136.8	1089.2	1058.4	1027.6	948.7	856.9	760.6	672.3	598.0	538.8
132.5°	1135.6	1102.0	1055.5	1024.8	994.0	917.3	832.6	749.0	671.2	606.1	553.9
135°	1093.8	1061.3	1014.9	985.8	956.8	886.0	810.5	737.3	670.0	614.3	566.7
137.5°	1048.5	1014.9	970.7	944.0	917.3	855.8	789.6	726.9	670.0	618.9	575.9
140°	994.0	968.4	927.8	903.4	879.0	826.8	772.2	718.8	668.8	624.7	585.2
142.5°	944.0	920.8	886.0	865.6	845.3	802.4	755.9	711.8	668.8	629.4	592.2
145°	896.4	876.7	847.7	831.4	815.1	780.3	740.8	703.7	666.5	630.5	596.8
147.5°	855.8	838.4	816.3	803.0	789.6	760.6	728.1	696.7	663.0	631.7	601.5
150°	820.9	805.9	787.3	776.8	766.4	743.2	716.4	688.6	659.5	631.7	605.0
152.5°	789.6	778.0	762.9	754.8	746.6	725.7	703.7	679.3	653.7	629.4	607.3
155°	761.7	752.4	740.8	733.8	726.9	709.5	690.9	670.0	647.9	627.0	608.5
157.5°	736.2	729.2	719.9	714.1	708.3	693.2	677.0	660.7	642.1	624.7	608.5
160°	713.0	706.0	699.0	694.4	689.7	677.0	664.2	650.3	635.2	621.2	608.5
162.5°	690.9	683.9	679.3	675.2	671.2	661.9	651.4	641.0	628.2	617.7	608.5
165°	670.0	665.4	660.7	657.8	654.9	646.8	639.8	630.5	621.2	613.1	606.1
167.5°	650.3	646.8	644.5	642.8	641.0	634.0	628.2	621.2	614.3	608.5	603.8
170°	632.8	631.7	629.4	627.6	625.9	621.2	617.7	611.9	607.3	603.8	601.5
172.5°	617.7	616.6	615.4	614.2	613.1	610.8	608.5	603.8	600.3	599.2	599.2
175°	606.1	603.8	603.8	603.8	603.8	601.5	600.3	598.0	595.7	595.7	596.8
177.5°	596.8	595.7	596.8	596.2	595.7	595.7	594.5	593.4	592.2	592.2	594.5
180°	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1749.4	1742.5	1738.4	1737.0	1724.6	1717.7	1713.6	1710.9	1706.8	1695.8	1686.1
5°	1815.3	1796.1	1786.5	1775.5	1756.2	1734.2	1716.4	1705.4	1691.6	1669.7	1649.0
7.5°	1877.2	1848.3	1829.1	1813.9	1781.0	1745.2	1716.4	1693.0	1666.9	1636.7	1607.8
10°	1941.7	1895.0	1870.3	1846.9	1798.8	1752.1	1710.9	1676.5	1639.4	1599.6	1568.0
12.5°	1992.6	1930.7	1903.3	1870.3	1811.2	1756.2	1704.0	1657.3	1609.2	1566.6	1521.2
15°	2051.7	1974.7	1943.1	1900.5	1819.4	1748.0	1680.6	1629.8	1580.3	1517.1	1469.0
17.5°	2086.0	1996.7	1951.4	1914.3	1826.3	1739.7	1661.4	1598.2	1540.5	1477.3	1426.4
20°	2120.4	2018.7	1967.9	1915.6	1811.2	1719.1	1636.7	1561.1	1500.6	1431.9	1379.7
22.5°	2131.4	2013.2	1959.6	1911.5	1801.6	1698.5	1603.7	1526.7	1456.6	1387.9	1328.8
25°	2131.4	2011.8	1948.6	1886.8	1771.3	1665.5	1570.7	1486.9	1408.6	1339.8	1280.8
27.5°	2109.4	1984.3	1918.4	1862.0	1742.5	1628.4	1530.9	1438.8	1363.2	1294.5	1227.2
30°	2081.9	1944.5	1878.5	1811.2	1695.8	1587.2	1481.4	1396.2	1316.5	1238.2	1177.7
32.5°	2047.6	1901.9	1829.1	1760.3	1638.0	1525.4	1427.8	1344.0	1268.4	1187.3	1120.0
35°	1998.1	1838.7	1757.6	1697.1	1579.0	1462.1	1368.7	1286.2	1213.4	1129.6	1056.8
37.5°	1934.9	1781.0	1698.5	1624.3	1502.0	1394.8	1306.9	1227.2	1155.7	1078.7	997.7
40°	1860.7	1699.9	1628.4	1550.1	1420.9	1319.2	1236.8	1165.3	1093.9	1021.0	942.7
42.5°	1776.8	1617.4	1537.7	1462.1	1338.5	1238.2	1161.2	1096.6	1030.6	963.3	879.5
45°	1676.5	1526.7	1449.8	1378.3	1258.8	1155.7	1085.6	1023.8	967.4	898.7	824.5
47.5°	1563.8	1433.3	1355.0	1278.0	1161.2	1071.9	1003.2	950.9	902.8	834.1	766.8
50°	1453.9	1324.7	1261.5	1183.2	1076.0	992.2	922.1	878.1	841.0	773.7	713.2
52.5°	1315.1	1217.5	1157.1	1089.7	986.7	901.5	846.5	808.0	764.1	711.8	658.2
55°	1192.8	1102.1	1054.0	990.8	889.1	813.5	766.8	731.1	696.7	650.0	607.4
57.5°	1054.0	997.7	949.6	894.6	794.3	729.7	688.5	658.2	626.6	588.2	553.8
60°	908.3	882.2	835.5	791.5	706.3	650.0	615.6	588.2	557.9	526.3	497.5
62.5°	779.2	764.1	736.6	702.2	622.5	574.4	540.1	519.4	497.5	468.6	441.1
65°	656.9	650.0	623.9	599.2	544.2	501.6	471.3	459.0	434.2	412.3	387.5
67.5°	548.3	540.1	524.9	514.0	467.2	427.4	412.3	395.8	375.2	358.7	338.1
70°	438.4	437.0	427.4	413.6	388.9	360.0	344.9	333.9	313.3	300.9	285.8
72.5°	340.8	347.7	339.4	333.9	317.4	296.8	283.1	276.2	259.7	250.1	239.1
75°	254.2	259.7	263.8	254.2	250.1	240.5	228.1	221.2	213.0	199.3	195.1
77.5°	173.1	185.5	185.5	188.3	189.6	184.1	174.5	169.0	159.4	156.7	151.2
80°	114.1	125.1	126.4	129.2	133.3	133.3	126.4	125.1	115.4	114.1	109.9
82.5°	66.0	75.6	81.1	85.2	83.8	89.3	83.8	82.5	77.0	77.0	74.2
85°	35.7	37.1	39.9	42.6	45.3	48.1	48.1	46.7	45.3	44.0	41.2
87.5°	13.7	13.7	15.1	13.7	15.1	17.9	19.2	19.2	17.9	16.5	13.7
90°	16.3	9.3	9.3	9.3	8.1	7.0	3.5	1.2	3.5	7.0	8.1
92.5°	176.5	104.5	89.4	74.3	53.4	36.0	23.2	16.3	23.2	36.0	53.4
95°	246.2	145.1	120.8	96.4	68.5	53.4	41.8	38.3	41.8	53.4	68.5
97.5°	234.6	154.4	133.5	112.6	88.2	74.3	63.9	63.9	63.9	74.3	88.2
100°	238.0	169.5	151.0	132.4	110.3	96.4	88.2	88.2	88.2	96.4	110.3
102.5°	249.7	189.3	171.9	154.4	133.5	120.8	113.8	111.5	113.8	120.8	133.5
105°	269.4	213.7	196.8	180.0	159.1	145.1	139.3	135.9	139.3	145.1	159.1
107.5°	290.3	239.2	222.4	205.5	185.8	170.7	164.9	162.6	164.9	170.7	185.8
110°	314.7	263.6	247.9	232.2	211.3	197.4	191.6	189.3	191.6	197.4	211.3

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	337.9	289.1	273.5	257.8	236.9	224.1	217.1	214.8	217.1	224.1	236.9
115°	362.3	315.8	300.2	284.5	262.4	250.8	242.7	239.2	242.7	250.8	262.4
117.5°	385.5	341.4	325.2	308.9	288.0	275.2	268.2	264.7	268.2	275.2	288.0
120°	409.9	365.8	349.6	333.3	313.5	300.7	292.6	290.3	292.6	300.7	313.5
122.5°	433.1	389.0	373.3	357.6	335.6	324.0	315.8	313.5	315.8	324.0	335.6
125°	454.0	412.2	396.0	379.7	357.6	344.9	337.9	333.3	337.9	344.9	357.6
127.5°	473.8	433.1	416.8	400.6	377.4	363.4	355.3	351.8	355.3	363.4	377.4
130°	493.5	454.0	437.2	420.3	398.3	380.9	371.6	366.9	371.6	380.9	398.3
132.5°	509.8	470.3	454.6	438.9	414.5	398.3	385.5	382.0	385.5	398.3	414.5
135°	524.9	486.5	471.4	456.3	432.0	412.2	400.6	396.0	400.6	412.2	432.0
137.5°	536.5	500.5	486.0	471.4	445.9	427.3	414.5	409.9	414.5	427.3	445.9
140°	548.1	513.2	499.3	485.4	461.0	441.2	428.5	425.0	428.5	441.2	461.0
142.5°	558.5	524.9	511.5	498.1	474.9	456.3	444.7	441.2	444.7	456.3	474.9
145°	565.5	535.3	522.6	509.8	487.7	471.4	459.8	456.3	459.8	471.4	487.7
147.5°	573.6	544.6	533.0	521.4	502.8	485.4	474.9	473.8	474.9	485.4	502.8
150°	579.4	553.9	542.8	531.8	514.4	500.5	491.2	490.0	491.2	500.5	514.4
152.5°	584.1	562.0	552.2	542.3	527.2	514.4	505.1	505.1	505.1	514.4	527.2
155°	588.7	569.0	560.3	551.6	538.8	527.2	520.2	519.0	520.2	527.2	538.8
157.5°	592.2	574.8	567.8	560.8	549.2	539.9	533.0	533.0	533.0	539.9	549.2
160°	594.5	580.6	574.2	567.8	558.5	550.4	545.8	545.8	545.8	550.4	558.5
162.5°	596.8	584.1	579.4	574.8	566.7	559.7	556.2	557.4	556.2	559.7	566.7
165°	596.8	586.4	582.9	579.4	573.6	567.8	565.5	565.5	565.5	567.8	573.6
167.5°	596.8	588.7	585.8	582.9	579.4	574.8	573.6	574.8	573.6	574.8	579.4
170°	595.7	589.9	588.2	586.4	584.1	580.6	579.4	580.6	579.4	580.6	584.1
172.5°	594.5	591.0	589.8	588.7	587.6	585.2	585.2	586.4	585.2	585.2	587.6
175°	593.4	591.0	591.0	591.0	589.9	588.7	588.7	589.9	588.7	588.7	589.9
177.5°	592.2	591.0	591.0	591.0	591.0	589.9	591.0	592.2	591.0	589.9	591.0
180°	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1677.9	1675.1	1672.4	1661.4	1651.8	1635.3	1621.6	1616.1	1614.7	1616.1	1611.9
5°	1629.8	1628.4	1618.8	1599.6	1581.7	1562.5	1548.7	1535.0	1526.7	1526.7	1517.1
7.5°	1584.5	1574.8	1566.6	1541.9	1521.2	1495.1	1474.5	1462.1	1455.3	1440.2	1440.2
10°	1536.4	1522.6	1511.6	1488.3	1458.0	1431.9	1405.8	1390.7	1378.3	1367.3	1363.2
12.5°	1488.3	1477.3	1456.6	1431.9	1401.7	1368.7	1341.2	1330.2	1301.4	1278.0	1279.4
15°	1442.9	1418.2	1408.6	1372.8	1337.1	1305.5	1265.6	1234.0	1210.7	1195.6	1176.3
17.5°	1392.1	1367.3	1349.5	1319.2	1272.5	1223.0	1184.6	1142.0	1118.6	1092.5	1080.1
20°	1335.7	1315.1	1301.4	1253.3	1196.9	1137.8	1095.2	1069.1	1043.0	1023.8	1012.8
22.5°	1287.6	1261.5	1245.0	1180.4	1118.6	1059.5	1026.5	1004.5	982.6	966.1	960.6
25°	1225.8	1210.7	1170.8	1114.5	1038.9	999.0	970.2	941.3	929.0	918.0	905.6
27.5°	1174.9	1137.8	1110.4	1036.1	989.4	944.1	915.2	893.2	878.1	867.1	857.5
30°	1111.7	1077.4	1038.9	977.1	934.5	891.9	865.7	847.9	831.4	824.5	816.3
32.5°	1045.8	1014.2	977.1	927.6	875.4	842.4	821.8	802.5	791.5	784.7	775.0
35°	986.7	946.8	922.1	875.4	832.8	795.7	776.4	759.9	747.6	744.8	743.4
37.5°	923.5	893.2	869.9	821.8	786.0	754.4	736.6	718.7	711.8	710.5	705.0
40°	868.5	842.4	820.4	775.0	736.6	707.7	694.0	683.0	676.1	676.1	674.7
42.5°	820.4	792.9	770.9	729.7	695.3	669.2	654.1	643.1	640.4	641.8	640.4
45°	766.8	743.4	721.5	678.9	650.0	630.8	614.3	608.8	604.6	606.0	607.4
47.5°	716.0	696.7	674.7	640.4	607.4	586.8	577.2	571.7	571.7	571.7	574.4
50°	670.6	648.6	629.4	593.7	563.4	546.9	538.7	531.8	533.2	534.6	535.9
52.5°	617.0	597.8	584.0	548.3	526.3	505.7	496.1	497.5	496.1	496.1	498.8
55°	570.3	551.1	537.3	504.3	482.3	468.6	460.4	456.2	457.6	454.9	460.4
57.5°	518.1	501.6	492.0	460.4	441.1	428.7	421.9	415.0	417.8	416.4	415.0
60°	472.7	453.5	438.4	416.4	399.9	384.8	380.7	373.8	376.5	373.8	372.4
62.5°	420.5	405.4	394.4	372.4	358.7	346.3	336.7	332.6	331.2	327.1	322.9
65°	368.3	360.0	349.0	327.1	313.3	303.7	298.2	294.1	292.7	281.7	269.3
67.5°	320.2	314.7	303.7	287.2	274.8	265.2	257.0	250.1	241.9	233.6	226.7
70°	274.8	266.6	259.7	244.6	233.6	224.0	215.7	207.5	203.4	195.1	192.4
72.5°	230.9	222.6	215.7	202.0	192.4	182.8	180.0	170.4	166.3	164.9	164.9
75°	185.5	178.6	174.5	162.2	153.9	147.0	142.9	140.2	137.4	134.7	130.5
77.5°	141.5	137.4	134.7	126.4	119.6	115.4	114.1	104.4	101.7	98.9	96.2
80°	103.1	101.7	98.9	92.1	89.3	79.7	79.7	77.0	75.6	75.6	75.6
82.5°	70.1	67.3	66.0	59.1	57.7	56.3	55.0	53.6	55.0	53.6	55.0
85°	37.1	35.7	34.4	34.4	34.4	34.4	34.4	34.4	34.4	33.0	34.4
87.5°	13.7	13.7	13.7	13.7	12.4	13.7	13.7	12.4	13.7	13.7	13.7
90°	9.3	9.3	9.3	16.3	16.3	18.6	20.9	19.7	20.9	22.1	23.2
92.5°	74.3	89.4	104.5	176.5	289.1	398.3	455.2	378.5	279.8	209.0	164.9
95°	96.4	120.8	145.1	246.2	436.6	714.1	946.4	973.1	860.4	680.4	524.9
97.5°	112.6	133.5	154.4	234.6	398.3	683.9	1012.5	1220.4	1239.0	1149.6	1021.8
100°	132.4	151.0	169.5	238.0	369.3	606.1	933.6	1230.8	1400.4	1423.6	1366.7
102.5°	154.4	171.9	189.3	249.7	361.1	553.9	834.9	1143.8	1392.2	1530.4	1565.3
105°	180.0	196.8	213.7	269.4	365.8	528.3	761.7	1034.6	1300.5	1501.4	1616.4
107.5°	205.5	222.4	239.2	290.3	379.7	521.4	714.1	945.2	1187.9	1405.0	1565.3
110°	232.2	247.9	263.6	314.7	396.0	523.7	692.1	881.3	1088.0	1288.9	1457.3

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	257.8	273.5	289.1	337.9	413.4	530.7	681.6	845.3	1014.9	1186.7	1343.5
115°	284.5	300.2	315.8	362.3	432.0	539.9	679.3	825.6	970.7	1113.6	1249.4
117.5°	308.9	325.2	341.4	385.5	450.5	549.2	678.1	815.1	945.2	1066.0	1176.3
120°	333.3	349.6	365.8	409.9	470.3	559.7	678.1	807.0	928.9	1036.9	1129.8
122.5°	357.6	373.3	389.0	433.1	488.9	570.1	677.0	797.7	915.0	1018.3	1100.8
125°	379.7	396.0	412.2	454.0	507.4	580.6	675.8	787.3	898.7	998.6	1078.7
127.5°	400.6	416.8	433.1	473.8	523.7	588.7	673.5	773.3	880.2	976.5	1056.7
130°	420.3	437.2	454.0	493.5	538.8	598.0	672.3	760.6	856.9	948.7	1027.6
132.5°	438.9	454.6	470.3	509.8	553.9	606.1	671.2	749.0	832.6	917.3	994.0
135°	456.3	471.4	486.5	524.9	566.7	614.3	670.0	737.3	810.5	886.0	956.8
137.5°	471.4	486.0	500.5	536.5	575.9	618.9	670.0	726.9	789.6	855.8	917.3
140°	485.4	499.3	513.2	548.1	585.2	624.7	668.8	718.8	772.2	826.8	879.0
142.5°	498.1	511.5	524.9	558.5	592.2	629.4	668.8	711.8	755.9	802.4	845.3
145°	509.8	522.6	535.3	565.5	596.8	630.5	666.5	703.7	740.8	780.3	815.1
147.5°	521.4	533.0	544.6	573.6	601.5	631.7	663.0	696.7	728.1	760.6	789.6
150°	531.8	542.8	553.9	579.4	605.0	631.7	659.5	688.6	716.4	743.2	766.4
152.5°	542.3	552.2	562.0	584.1	607.3	629.4	653.7	679.3	703.7	725.7	746.6
155°	551.6	560.3	569.0	588.7	608.5	627.0	647.9	670.0	690.9	709.5	726.9
157.5°	560.8	567.8	574.8	592.2	608.5	624.7	642.1	660.7	677.0	693.2	708.3
160°	567.8	574.2	580.6	594.5	608.5	621.2	635.2	650.3	664.2	677.0	689.7
162.5°	574.8	579.4	584.1	596.8	608.5	617.7	628.2	641.0	651.4	661.9	671.2
165°	579.4	582.9	586.4	596.8	606.1	613.1	621.2	630.5	639.8	646.8	654.9
167.5°	582.9	585.8	588.7	596.8	603.8	608.5	614.3	621.2	628.2	634.0	641.0
170°	586.4	588.2	589.9	595.7	601.5	603.8	607.3	611.9	617.7	621.2	625.9
172.5°	588.7	589.8	591.0	594.5	599.2	599.2	600.3	603.8	608.5	610.8	613.1
175°	591.0	591.0	591.0	593.4	596.8	595.7	595.7	598.0	600.3	601.5	603.8
177.5°	591.0	591.0	591.0	592.2	594.5	592.2	592.2	593.4	594.5	595.7	595.7
180°	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1611.9	1617.4	1610.6	1614.7	1605.1	1603.7	1605.1	1605.1	1606.4	1607.8	1609.2
5°	1521.2	1519.9	1511.6	1506.1	1502.0	1506.1	1508.9	1511.6	1508.9	1511.6	1513.0
7.5°	1436.0	1431.9	1427.8	1418.2	1420.9	1418.2	1426.4	1422.3	1422.3	1429.2	1434.7
10°	1360.5	1352.2	1349.5	1338.5	1330.2	1328.8	1338.5	1342.6	1346.7	1349.5	1360.5
12.5°	1262.9	1250.5	1240.9	1245.0	1221.7	1231.3	1234.0	1228.5	1245.0	1264.3	1253.3
15°	1158.4	1159.8	1140.6	1133.7	1114.5	1120.0	1121.3	1135.1	1148.8	1147.5	1163.9
17.5°	1081.5	1073.2	1056.8	1055.4	1047.1	1051.3	1049.9	1060.9	1056.8	1063.6	1077.4
20°	1010.0	1004.5	990.8	985.3	988.0	985.3	986.7	988.0	992.2	1007.3	1004.5
22.5°	953.7	946.8	946.8	940.0	931.7	929.0	935.8	940.0	945.4	948.2	955.1
25°	904.2	898.7	891.9	887.7	880.9	882.2	886.4	891.9	896.0	901.5	907.0
27.5°	853.4	853.4	846.5	845.1	842.4	841.0	846.5	849.3	849.3	853.4	858.9
30°	813.5	813.5	806.7	805.3	803.9	803.9	808.0	809.4	810.8	814.9	817.6
32.5°	775.0	773.7	770.9	772.3	770.9	772.3	772.3	773.7	776.4	777.8	783.3
35°	739.3	740.7	737.9	737.9	736.6	737.9	740.7	742.1	743.4	746.2	746.2
37.5°	705.0	707.7	706.3	710.5	710.5	710.5	710.5	713.2	713.2	713.2	711.8
40°	674.7	674.7	673.4	676.1	678.9	678.9	680.2	680.2	681.6	681.6	680.2
42.5°	640.4	643.1	647.2	648.6	651.4	650.0	654.1	652.7	654.1	651.4	648.6
45°	608.8	608.8	614.3	619.8	621.1	621.1	621.1	623.9	621.1	617.0	615.6
47.5°	574.4	577.2	579.9	586.8	588.2	588.2	588.2	588.2	585.4	585.4	585.4
50°	540.1	541.4	542.8	545.6	549.7	548.3	548.3	548.3	553.8	548.3	549.7
52.5°	498.8	500.2	501.6	507.1	505.7	505.7	507.1	507.1	511.2	509.8	507.1
55°	457.6	457.6	460.4	460.4	460.4	463.1	464.5	467.2	465.9	467.2	468.6
57.5°	416.4	413.6	412.3	412.3	416.4	415.0	416.4	416.4	421.9	424.6	426.0
60°	368.3	368.3	366.9	358.7	358.7	357.3	361.4	364.2	366.9	379.3	377.9
62.5°	318.8	313.3	307.8	309.2	300.9	305.1	302.3	305.1	313.3	322.9	324.3
65°	269.3	265.2	259.7	258.3	255.6	259.7	258.3	259.7	263.8	269.3	276.2
67.5°	225.4	224.0	221.2	219.9	219.9	219.9	222.6	222.6	224.0	228.1	232.2
70°	192.4	191.0	192.4	189.6	191.0	189.6	191.0	192.4	193.8	195.1	199.3
72.5°	162.2	162.2	162.2	159.4	162.2	160.8	160.8	162.2	163.5	164.9	167.7
75°	129.2	126.4	123.7	120.9	119.6	122.3	123.7	122.3	126.4	131.9	131.9
77.5°	97.6	96.2	96.2	96.2	97.6	96.2	98.9	97.6	98.9	98.9	101.7
80°	75.6	74.2	75.6	75.6	74.2	77.0	75.6	75.6	77.0	78.3	77.0
82.5°	55.0	56.3	55.0	55.0	55.0	57.7	55.0	55.0	55.0	56.3	56.3
85°	34.4	34.4	34.4	34.4	35.7	34.4	35.7	34.4	37.1	35.7	35.7
87.5°	12.4	13.7	15.1	15.1	15.1	15.1	13.7	15.1	16.5	15.1	16.5
90°	23.2	23.2	24.4	25.5	24.4	24.4	24.4	25.5	24.4	23.2	23.2
92.5°	150.4	135.9	118.4	110.3	105.7	105.7	105.7	110.3	118.4	135.9	150.4
95°	468.6	412.2	355.3	319.3	298.4	283.3	298.4	319.3	355.3	412.2	468.6
97.5°	956.8	891.8	812.8	743.2	708.3	680.4	708.3	743.2	812.8	891.8	956.8
100°	1323.8	1280.8	1179.8	1108.9	1074.1	1064.8	1074.1	1108.9	1179.8	1280.8	1323.8
102.5°	1553.6	1542.0	1489.8	1443.3	1406.2	1399.2	1406.2	1443.3	1489.8	1542.0	1553.6
105°	1640.2	1664.0	1666.3	1657.0	1640.7	1633.8	1640.7	1657.0	1666.3	1664.0	1640.2
107.5°	1614.0	1662.8	1713.9	1734.8	1744.1	1745.2	1744.1	1734.8	1713.9	1662.8	1614.0
110°	1521.2	1585.0	1667.4	1716.2	1737.1	1747.6	1737.1	1716.2	1667.4	1585.0	1521.2

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1407.4	1471.2	1567.6	1629.1	1660.5	1679.1	1660.5	1629.1	1567.6	1471.2	1407.4
115°	1305.2	1360.9	1452.6	1522.3	1559.5	1568.7	1559.5	1522.3	1452.6	1360.9	1305.2
117.5°	1225.0	1273.8	1355.1	1415.5	1455.0	1460.8	1455.0	1415.5	1355.1	1273.8	1225.0
120°	1171.0	1212.3	1278.5	1329.5	1359.7	1372.5	1359.7	1329.5	1278.5	1212.3	1171.0
122.5°	1135.6	1170.5	1223.9	1265.7	1290.1	1302.8	1290.1	1265.7	1223.9	1170.5	1135.6
125°	1110.6	1142.6	1189.0	1222.7	1244.8	1251.7	1244.8	1222.7	1189.0	1142.6	1110.6
127.5°	1086.8	1117.0	1163.5	1193.7	1212.3	1219.2	1212.3	1193.7	1163.5	1117.0	1086.8
130°	1058.4	1089.2	1136.8	1165.8	1184.4	1191.4	1184.4	1165.8	1136.8	1089.2	1058.4
132.5°	1024.8	1055.5	1102.0	1135.6	1153.0	1160.0	1153.0	1135.6	1102.0	1055.5	1024.8
135°	985.8	1014.9	1061.3	1093.8	1112.4	1119.4	1112.4	1093.8	1061.3	1014.9	985.8
137.5°	944.0	970.7	1014.9	1048.5	1063.6	1071.8	1063.6	1048.5	1014.9	970.7	944.0
140°	903.4	927.8	968.4	994.0	1010.2	1019.5	1010.2	994.0	968.4	927.8	903.4
142.5°	865.6	886.0	920.8	944.0	958.0	963.8	958.0	944.0	920.8	886.0	865.6
145°	831.4	847.7	876.7	896.4	908.0	913.8	908.0	896.4	876.7	847.7	831.4
147.5°	803.0	816.3	838.4	855.8	865.1	867.4	865.1	855.8	838.4	816.3	803.0
150°	776.8	787.3	805.9	820.9	827.9	829.1	827.9	820.9	805.9	787.3	776.8
152.5°	754.8	762.9	778.0	789.6	793.1	794.2	793.1	789.6	778.0	762.9	754.8
155°	733.8	740.8	752.4	761.7	765.2	765.2	765.2	761.7	752.4	740.8	733.8
157.5°	714.1	719.9	729.2	736.2	738.5	738.5	738.5	736.2	729.2	719.9	714.1
160°	694.4	699.0	706.0	713.0	714.1	714.1	714.1	713.0	706.0	699.0	694.4
162.5°	675.2	679.3	683.9	690.9	692.1	690.9	692.1	690.9	683.9	679.3	675.2
165°	657.8	660.7	665.4	670.0	668.8	667.7	668.8	670.0	665.4	660.7	657.8
167.5°	642.8	644.5	646.8	650.3	650.3	649.1	650.3	650.3	646.8	644.5	642.8
170°	627.6	629.4	631.7	632.8	631.7	631.7	631.7	632.8	631.7	629.4	627.6
172.5°	614.2	615.4	616.6	617.7	616.6	614.3	616.6	617.7	616.6	615.4	614.2
175°	603.8	603.8	603.8	606.1	603.8	601.5	603.8	606.1	603.8	603.8	603.8
177.5°	596.2	596.8	595.7	596.8	594.5	592.2	594.5	596.8	595.7	596.8	596.2
180°	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1614.7	1621.6	1618.8	1609.2	1613.3	1621.6	1629.8	1640.8	1647.7	1653.2	1655.9
5°	1519.9	1532.2	1529.5	1529.5	1535.0	1548.7	1562.5	1585.8	1594.1	1603.7	1617.4
7.5°	1436.0	1445.7	1453.9	1456.6	1464.9	1482.8	1500.6	1526.7	1547.3	1558.3	1566.6
10°	1361.8	1368.7	1381.1	1387.9	1396.2	1418.2	1444.3	1471.8	1492.4	1511.6	1522.6
12.5°	1267.0	1294.5	1311.0	1322.0	1333.0	1366.0	1386.6	1416.8	1441.5	1459.4	1475.9
15°	1161.2	1194.2	1203.8	1246.4	1273.9	1300.0	1331.6	1367.3	1390.7	1411.3	1433.3
17.5°	1071.9	1095.2	1106.2	1151.6	1174.9	1216.2	1261.5	1306.9	1342.6	1357.7	1379.7
20°	1015.5	1027.9	1049.9	1065.0	1089.7	1137.8	1187.3	1242.3	1295.9	1311.0	1333.0
22.5°	957.8	974.3	989.4	1010.0	1029.3	1062.3	1111.7	1172.2	1229.9	1257.4	1283.5
25°	905.6	922.1	931.7	953.7	971.6	1004.5	1038.9	1100.7	1169.4	1192.8	1234.0
27.5°	864.4	874.0	890.5	900.1	920.7	950.9	982.6	1029.3	1096.6	1136.5	1176.3
30°	823.1	830.0	843.8	857.5	872.6	893.2	929.0	974.3	1036.1	1070.5	1110.4
32.5°	781.9	792.9	801.2	810.8	827.3	852.0	876.7	920.7	970.2	1008.7	1048.5
35°	747.6	751.7	762.7	773.7	784.7	806.7	832.8	875.4	919.3	949.6	985.3
37.5°	710.5	717.3	725.6	729.7	747.6	761.3	788.8	821.8	874.0	893.2	929.0
40°	681.6	680.2	688.5	695.3	703.6	725.6	742.1	777.8	819.0	849.3	871.2
42.5°	645.9	645.9	648.6	656.9	667.9	681.6	700.8	731.1	773.7	795.7	821.8
45°	617.0	612.9	614.3	619.8	626.6	640.4	659.6	685.7	728.3	746.2	773.7
47.5°	582.7	578.5	578.5	584.0	589.5	599.2	614.3	644.5	678.9	702.2	722.8
50°	544.2	545.6	544.2	548.3	551.1	560.7	577.2	601.9	633.5	652.7	676.1
52.5°	508.5	505.7	504.3	507.1	512.6	519.4	537.3	559.3	589.5	608.8	629.4
55°	464.5	467.2	467.2	467.2	475.5	478.2	492.0	514.0	544.2	559.3	578.5
57.5°	424.6	423.3	426.0	424.6	431.5	441.1	452.1	468.6	498.8	514.0	531.8
60°	380.7	382.0	383.4	383.4	388.9	398.5	410.9	426.0	450.7	465.9	482.3
62.5°	327.1	333.9	340.8	343.5	351.8	358.7	366.9	383.4	405.4	416.4	431.5
65°	276.2	285.8	295.5	302.3	307.8	314.7	325.7	340.8	358.7	369.7	384.8
67.5°	232.2	239.1	251.5	258.3	269.3	277.6	284.5	296.8	318.8	322.9	335.3
70°	200.6	203.4	208.9	214.4	226.7	233.6	241.9	254.2	270.7	280.3	287.2
72.5°	169.0	170.4	173.1	178.6	184.1	192.4	202.0	213.0	228.1	232.2	241.9
75°	134.7	142.9	142.9	147.0	151.2	155.3	163.5	174.5	184.1	191.0	196.5
77.5°	100.3	104.4	107.2	114.1	119.6	123.7	129.2	137.4	142.9	148.4	152.5
80°	78.3	79.7	81.1	81.1	83.8	89.3	94.8	100.3	107.2	109.9	114.1
82.5°	57.7	57.7	57.7	60.5	61.8	63.2	63.2	66.0	72.8	75.6	79.7
85°	37.1	37.1	37.1	37.1	38.5	39.9	41.2	42.6	42.6	42.6	45.3
87.5°	15.1	17.9	16.5	17.9	17.9	17.9	17.9	19.2	19.2	20.6	20.6
90°	23.2	22.1	20.9	19.7	20.9	18.6	16.3	16.3	9.3	9.3	9.3
92.5°	164.9	209.0	279.8	378.5	455.2	398.3	289.1	176.5	104.5	89.4	74.3
95°	524.9	680.4	860.4	973.1	946.4	714.1	436.6	246.2	145.1	120.8	96.4
97.5°	1021.8	1149.6	1239.0	1220.4	1012.5	683.9	398.3	234.6	154.4	133.5	112.6
100°	1366.7	1423.6	1400.4	1230.8	933.6	606.1	369.3	238.0	169.5	151.0	132.4
102.5°	1565.3	1530.4	1392.2	1143.8	834.9	553.9	361.1	249.7	189.3	171.9	154.4
105°	1616.4	1501.4	1300.5	1034.6	761.7	528.3	365.8	269.4	213.7	196.8	180.0
107.5°	1565.3	1405.0	1187.9	945.2	714.1	521.4	379.7	290.3	239.2	222.4	205.5
110°	1457.3	1288.9	1088.0	881.3	692.1	523.7	396.0	314.7	263.6	247.9	232.2

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1343.5	1186.7	1014.9	845.3	681.6	530.7	413.4	337.9	289.1	273.5	257.8
115°	1249.4	1113.6	970.7	825.6	679.3	539.9	432.0	362.3	315.8	300.2	284.5
117.5°	1176.3	1066.0	945.2	815.1	678.1	549.2	450.5	385.5	341.4	325.2	308.9
120°	1129.8	1036.9	928.9	807.0	678.1	559.7	470.3	409.9	365.8	349.6	333.3
122.5°	1100.8	1018.3	915.0	797.7	677.0	570.1	488.9	433.1	389.0	373.3	357.6
125°	1078.7	998.6	898.7	787.3	675.8	580.6	507.4	454.0	412.2	396.0	379.7
127.5°	1056.7	976.5	880.2	773.3	673.5	588.7	523.7	473.8	433.1	416.8	400.6
130°	1027.6	948.7	856.9	760.6	672.3	598.0	538.8	493.5	454.0	437.2	420.3
132.5°	994.0	917.3	832.6	749.0	671.2	606.1	553.9	509.8	470.3	454.6	438.9
135°	956.8	886.0	810.5	737.3	670.0	614.3	566.7	524.9	486.5	471.4	456.3
137.5°	917.3	855.8	789.6	726.9	670.0	618.9	575.9	536.5	500.5	486.0	471.4
140°	879.0	826.8	772.2	718.8	668.8	624.7	585.2	548.1	513.2	499.3	485.4
142.5°	845.3	802.4	755.9	711.8	668.8	629.4	592.2	558.5	524.9	511.5	498.1
145°	815.1	780.3	740.8	703.7	666.5	630.5	596.8	565.5	535.3	522.6	509.8
147.5°	789.6	760.6	728.1	696.7	663.0	631.7	601.5	573.6	544.6	533.0	521.4
150°	766.4	743.2	716.4	688.6	659.5	631.7	605.0	579.4	553.9	542.8	531.8
152.5°	746.6	725.7	703.7	679.3	653.7	629.4	607.3	584.1	562.0	552.2	542.3
155°	726.9	709.5	690.9	670.0	647.9	627.0	608.5	588.7	569.0	560.3	551.6
157.5°	708.3	693.2	677.0	660.7	642.1	624.7	608.5	592.2	574.8	567.8	560.8
160°	689.7	677.0	664.2	650.3	635.2	621.2	608.5	594.5	580.6	574.2	567.8
162.5°	671.2	661.9	651.4	641.0	628.2	617.7	608.5	596.8	584.1	579.4	574.8
165°	654.9	646.8	639.8	630.5	621.2	613.1	606.1	596.8	586.4	582.9	579.4
167.5°	641.0	634.0	628.2	621.2	614.3	608.5	603.8	596.8	588.7	585.8	582.9
170°	625.9	621.2	617.7	611.9	607.3	603.8	601.5	595.7	589.9	588.2	586.4
172.5°	613.1	610.8	608.5	603.8	600.3	599.2	599.2	594.5	591.0	589.8	588.7
175°	603.8	601.5	600.3	598.0	595.7	595.7	596.8	593.4	591.0	591.0	591.0
177.5°	595.7	595.7	594.5	593.4	592.2	592.2	594.5	592.2	591.0	591.0	591.0
180°	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1705.4	1705.4	1705.4	1705.4
2.5°	1666.9	1675.1	1688.9	1708.1
5°	1628.4	1651.8	1673.8	1702.6
7.5°	1594.1	1621.6	1651.8	1693.0
10°	1554.2	1588.6	1627.1	1677.9
12.5°	1507.5	1555.6	1599.6	1654.5
15°	1473.1	1508.9	1565.2	1629.8
17.5°	1425.0	1473.1	1529.5	1602.3
20°	1379.7	1430.5	1493.8	1569.3
22.5°	1331.6	1389.3	1452.5	1533.6
25°	1282.1	1344.0	1407.2	1493.8
27.5°	1236.8	1293.1	1364.6	1452.5
30°	1181.8	1246.4	1315.1	1407.2
32.5°	1128.2	1195.6	1265.6	1357.7
35°	1070.5	1137.8	1214.8	1302.7
37.5°	1014.2	1088.4	1158.4	1243.6
40°	952.3	1029.3	1102.1	1188.7
42.5°	891.9	971.6	1044.4	1118.6
45°	835.5	913.8	979.8	1049.9
47.5°	781.9	852.0	919.3	982.6
50°	729.7	788.8	850.6	902.8
52.5°	674.7	731.1	780.5	827.3
55°	625.3	669.2	713.2	755.8
57.5°	566.2	610.1	648.6	681.6
60°	516.7	544.2	581.3	615.6
62.5°	460.4	492.0	520.8	542.8
65°	405.4	432.9	454.9	474.1
67.5°	358.7	375.2	391.6	412.3
70°	302.3	316.1	335.3	350.4
72.5°	254.2	265.2	274.8	292.7
75°	206.1	215.7	221.2	237.7
77.5°	159.4	169.0	173.1	182.8
80°	122.3	123.7	129.2	137.4
82.5°	83.8	86.6	87.9	94.8
85°	48.1	55.0	53.6	56.3
87.5°	20.6	22.0	24.7	27.5
90°	8.1	7.0	3.5	1.2
92.5°	53.4	36.0	23.2	16.3
95°	68.5	53.4	41.8	38.3
97.5°	88.2	74.3	63.9	63.9
100°	110.3	96.4	88.2	88.2
102.5°	133.5	120.8	113.8	111.5
105°	159.1	145.1	139.3	135.9
107.5°	185.8	170.7	164.9	162.6
110°	211.3	197.4	191.6	189.3

TEST NUMBER: P1025967

CATALOG NUMBER: S124RDIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	236.9	224.1	217.1	214.8
115°	262.4	250.8	242.7	239.2
117.5°	288.0	275.2	268.2	264.7
120°	313.5	300.7	292.6	290.3
122.5°	335.6	324.0	315.8	313.5
125°	357.6	344.9	337.9	333.3
127.5°	377.4	363.4	355.3	351.8
130°	398.3	380.9	371.6	366.9
132.5°	414.5	398.3	385.5	382.0
135°	432.0	412.2	400.6	396.0
137.5°	445.9	427.3	414.5	409.9
140°	461.0	441.2	428.5	425.0
142.5°	474.9	456.3	444.7	441.2
145°	487.7	471.4	459.8	456.3
147.5°	502.8	485.4	474.9	473.8
150°	514.4	500.5	491.2	490.0
152.5°	527.2	514.4	505.1	505.1
155°	538.8	527.2	520.2	519.0
157.5°	549.2	539.9	533.0	533.0
160°	558.5	550.4	545.8	545.8
162.5°	566.7	559.7	556.2	557.4
165°	573.6	567.8	565.5	565.5
167.5°	579.4	574.8	573.6	574.8
170°	584.1	580.6	579.4	580.6
172.5°	587.6	585.2	585.2	586.4
175°	589.9	588.7	588.7	589.9
177.5°	591.0	589.9	591.0	592.2
180°	591.0	591.0	591.0	591.0

(END OF REPORT)