

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025979

Luminaire Tested: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025979
REPORT IS A COMBINATION OF REPORTS P998889 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8570.0 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	50	49	48
2	90	83	77	72	83	77	72	67	65	61	58	55	52	50	45	43	41
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36
4	75	65	57	51	69	60	54	48	52	47	42	44	40	37	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27
6	64	52	44	39	59	49	42	36	42	36	32	36	31	28	30	27	24
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	27	24	22
8	55	43	35	30	51	40	33	29	35	29	26	30	26	22	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13829	13829	13829	13829
5°	13830	15626	13852	11943
10°	13756	18013	13744	10387
15°	13591	20273	13591	8696
20°	13420	21981	13350	7658
25°	13211	22075	13150	6916
30°	12988	18771	12887	6406
35°	12675	14163	12514	6026
40°	12325	10264	12082	5730
45°	11746	7801	11455	5467
50°	11060	6304	10757	5082
55°	10317	5220	9979	4569
60°	9570	4414	9143	3800
65°	8635	3596	8358	3021
70°	7775	2916	7409	2454
75°	6813	2101	6340	1798
80°	5622	1392	5116	1321
85°	4075	717	3384	717

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 17312 cd/sqm

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.2	1.9
10°-20°	495.9	5.8
20°-30°	776.8	9.1
30°-40°	862.6	10.1
40°-50°	764.4	8.9
50°-60°	595.7	7.0
60°-70°	389.7	4.5
70°-80°	191.2	2.2
80°-90°	48.9	0.6
90°-100°	426.0	5.0
100°-110°	889.3	10.4
110°-120°	790.5	9.2
120°-130°	665.5	7.8
130°-140°	555.2	6.5
140°-150°	423.9	4.9
150°-160°	298.0	3.5
160°-170°	175.3	2.0
170°-180°	57.0	0.7
0°-30°	1436.9	16.8
0°-40°	2299.5	26.8
0°-60°	3659.6	42.7
0°-90°	4289.3	50.1
90°-120°	2105.8	24.6
90°-150°	3750.4	43.8
90°-180°	4281.0	50.0
0°-180°	8570.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1696	1696	1696	1696	1696	
5°	1693	1960	1696	1498	1693	161
15°	1621	2596	1621	1114	1621	457
25°	1485	2800	1479	877	1485	685
35°	1296	1725	1279	734	1296	810
45°	1044	881	1018	618	1044	805
55°	752	526	727	460	752	672
65°	472	308	456	258	472	470
75°	236	142	220	122	236	251
85°	56	34	46	34	56	63
90°	1	24	1	24	1	6
95°	38	282	38	282	38	42
105°	135	1625	135	1625	135	144
115°	238	1560	238	1560	238	236
125°	331	1245	331	1245	331	295
135°	394	1113	394	1113	394	304
145°	454	909	454	909	454	285
155°	516	761	516	761	516	238
165°	562	664	562	664	562	159
175°	587	598	587	598	587	56
180°	588	588	588	588	588	

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9
2.5°	1698.6	1713.7	1721.9	1728.7	1742.3	1747.8	1758.7	1761.5	1772.4	1771.0	1766.9
5°	1693.2	1719.1	1738.2	1758.7	1783.3	1797.0	1812.0	1833.9	1844.8	1859.9	1869.4
7.5°	1683.6	1719.1	1750.5	1782.0	1821.6	1843.5	1862.6	1896.8	1925.5	1950.1	1977.4
10°	1668.6	1713.7	1760.1	1802.5	1857.1	1883.1	1911.8	1962.4	2002.0	2036.2	2079.9
12.5°	1645.3	1708.2	1760.1	1817.5	1887.2	1922.7	1961.0	2021.1	2067.6	2123.6	2178.3
15°	1620.7	1690.4	1758.7	1833.9	1913.2	1954.2	1992.4	2073.1	2144.1	2208.3	2268.5
17.5°	1593.4	1669.9	1745.1	1828.4	1924.1	1974.7	2019.8	2116.8	2194.7	2278.0	2338.2
20°	1560.6	1644.0	1730.0	1823.0	1930.9	1987.0	2037.5	2148.2	2234.3	2324.5	2399.7
22.5°	1525.1	1615.3	1709.6	1810.7	1922.7	1984.2	2043.0	2161.9	2261.6	2345.0	2446.1
25°	1485.4	1581.1	1678.1	1784.7	1910.4	1977.4	2037.5	2155.0	2261.6	2371.0	2469.4
27.5°	1444.4	1542.8	1644.0	1756.0	1884.5	1950.1	2018.4	2131.8	2256.2	2375.1	2474.8
30°	1399.3	1495.0	1601.6	1708.2	1844.8	1910.4	1980.1	2103.1	2238.4	2357.3	2465.3
32.5°	1350.1	1448.5	1549.7	1660.4	1794.3	1865.3	1929.6	2069.0	2207.0	2324.5	2425.6
35°	1295.5	1388.4	1484.1	1597.5	1730.0	1794.3	1870.8	2015.7	2155.0	2279.4	2345.0
37.5°	1236.7	1325.6	1414.4	1526.4	1653.5	1731.4	1806.6	1952.8	2100.4	2183.7	2217.9
40°	1182.1	1260.0	1337.9	1445.8	1574.3	1654.9	1731.4	1883.1	2012.9	2077.2	2051.2
42.5°	1112.4	1193.0	1262.7	1362.4	1492.3	1567.4	1645.3	1802.5	1907.7	1933.7	1869.4
45°	1044.0	1111.0	1178.0	1275.0	1411.6	1475.9	1559.2	1705.5	1792.9	1769.7	1675.4
47.5°	977.1	1031.7	1094.6	1188.9	1311.9	1388.4	1466.3	1593.4	1654.9	1622.1	1490.9
50°	897.8	952.5	1018.1	1100.1	1219.0	1292.8	1354.2	1471.8	1518.2	1437.6	1279.1
52.5°	822.7	870.5	926.5	1003.0	1116.5	1183.4	1250.4	1351.5	1366.5	1273.6	1106.9
55°	751.6	789.9	848.6	910.1	1014.0	1085.0	1131.5	1217.6	1213.5	1097.3	953.9
57.5°	677.8	713.3	753.0	817.2	915.6	968.9	1019.4	1094.6	1055.0	956.6	814.5
60°	612.2	632.7	672.3	733.8	817.2	863.7	903.3	944.3	910.1	803.5	694.2
62.5°	539.8	563.0	591.7	640.9	714.7	758.4	787.1	804.9	769.4	687.4	587.6
65°	471.5	492.0	522.0	565.8	621.8	654.6	669.6	681.9	662.8	569.9	490.6
67.5°	410.0	423.6	451.0	479.7	539.8	548.0	568.5	574.0	535.7	464.6	401.8
70°	348.5	362.1	374.4	408.6	435.9	451.0	455.1	455.1	416.8	370.3	318.4
72.5°	291.1	299.3	311.6	334.8	349.8	360.8	366.2	359.4	323.9	285.6	247.3
75°	236.4	240.5	251.4	266.5	278.8	274.7	273.3	265.1	239.1	211.8	190.0
77.5°	181.8	184.5	196.8	200.9	200.9	205.0	199.5	191.3	169.5	149.0	139.4
80°	136.7	140.8	142.1	144.9	142.1	142.1	138.0	124.4	113.4	103.9	97.0
82.5°	94.3	97.0	98.4	94.3	97.0	92.9	86.1	76.5	69.7	68.3	65.6
85°	56.0	57.4	56.0	56.0	51.9	50.6	45.1	43.7	41.0	41.0	39.6
87.5°	27.3	26.0	23.2	20.5	20.5	19.1	20.5	17.8	20.5	19.1	17.8
90°	1.2	3.5	6.9	8.1	9.2	9.2	9.2	16.2	16.2	18.5	20.8
92.5°	16.2	23.1	35.8	53.1	73.9	88.9	103.9	175.5	287.5	396.1	452.6
95°	38.1	41.6	53.1	68.1	95.8	120.0	144.3	244.8	434.2	710.1	941.1
97.5°	63.5	63.5	73.9	87.8	112.0	132.8	153.6	233.3	396.1	680.1	1006.9
100°	87.8	87.8	95.8	109.7	131.6	150.1	168.6	236.7	367.2	602.8	928.4
102.5°	110.9	113.2	120.1	132.8	153.6	170.9	188.2	248.3	359.1	550.8	830.2
105°	135.1	138.6	144.3	158.2	179.0	195.8	212.5	267.9	363.7	525.4	757.5
107.5°	161.7	164.0	169.7	184.8	204.4	221.2	237.9	288.7	377.6	518.5	710.1
110°	188.2	190.5	196.3	210.2	230.9	246.5	262.1	312.9	393.8	520.8	688.2

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	213.6	215.9	222.9	235.6	256.3	271.9	287.5	336.0	411.1	527.7	677.8
115°	237.9	241.3	249.4	261.0	282.9	298.5	314.1	360.3	429.5	536.9	675.5
117.5°	263.3	266.7	273.7	286.4	307.2	323.4	339.5	383.4	448.0	546.2	674.3
120°	288.7	291.0	299.1	311.8	331.4	347.5	363.7	407.6	467.7	556.6	674.3
122.5°	311.8	314.1	322.2	333.7	355.6	371.2	386.8	430.7	486.1	567.0	673.2
125°	331.4	336.0	342.9	355.6	377.6	393.8	409.9	451.5	504.6	577.4	672.0
127.5°	349.9	353.3	361.4	375.3	398.4	414.6	430.7	471.1	520.8	585.4	669.7
130°	364.9	369.5	378.7	396.1	418.0	434.8	451.5	490.7	535.8	594.7	668.6
132.5°	379.9	383.4	396.1	412.2	436.5	452.1	467.7	506.9	550.8	602.8	667.4
135°	393.8	398.4	409.9	429.5	453.8	468.8	483.8	521.9	563.5	610.8	666.3
137.5°	407.6	412.2	424.9	443.4	468.8	483.2	497.7	533.5	572.7	615.5	666.3
140°	422.6	426.1	438.8	458.4	482.7	496.6	510.4	545.0	582.0	621.2	665.1
142.5°	438.8	442.3	453.8	472.3	495.4	508.6	521.9	555.4	588.9	625.8	665.1
145°	453.8	457.3	468.8	485.0	506.9	519.6	532.3	562.3	593.5	627.0	662.8
147.5°	471.1	472.3	482.7	500.0	518.5	530.0	541.6	570.4	598.1	628.2	659.3
150°	487.3	488.4	497.7	511.5	528.9	539.8	550.8	576.2	601.6	628.2	655.9
152.5°	502.3	502.3	511.5	524.2	539.2	549.0	558.9	580.8	603.9	625.8	650.1
155°	516.2	517.3	524.2	535.8	548.5	557.2	565.8	585.4	605.1	623.5	644.3
157.5°	530.0	530.0	536.9	546.2	557.7	564.7	571.6	588.9	605.1	621.2	638.6
160°	542.7	542.7	547.3	555.4	564.6	571.0	577.4	591.2	605.1	617.8	631.6
162.5°	554.3	553.1	556.6	563.5	571.6	576.2	580.8	593.5	605.1	614.3	624.7
165°	562.3	562.3	564.6	570.4	576.2	579.7	583.1	593.5	602.8	609.7	617.8
167.5°	571.6	570.4	571.6	576.2	579.7	582.6	585.4	593.5	600.4	605.1	610.8
170°	577.4	576.2	577.4	580.8	583.1	584.8	586.6	592.4	598.1	600.4	603.9
172.5°	583.1	582.0	582.0	584.3	585.4	586.6	587.7	591.2	595.8	595.8	597.0
175°	586.6	585.4	585.4	586.6	587.7	587.7	587.7	590.1	593.5	592.4	592.4
177.5°	588.9	587.7	586.6	587.7	587.7	587.7	587.7	588.9	591.2	588.9	588.9
180°	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9
2.5°	1777.9	1792.9	1794.3	1807.9	1803.8	1797.0	1809.3	1801.1	1817.5	1812.0	1818.9
5°	1881.7	1902.2	1920.0	1930.9	1950.1	1946.0	1966.5	1959.6	1974.7	1959.6	1978.8
7.5°	2003.4	2037.5	2055.3	2084.0	2092.2	2093.6	2118.1	2123.6	2133.2	2123.6	2134.5
10°	2122.2	2163.2	2204.2	2227.5	2242.5	2263.0	2284.9	2294.4	2301.3	2291.7	2298.5
12.5°	2230.2	2294.4	2339.5	2386.0	2396.9	2414.7	2437.9	2435.2	2462.5	2457.1	2469.4
15°	2330.0	2401.0	2455.7	2492.6	2522.6	2537.7	2581.4	2584.1	2582.8	2596.4	2588.2
17.5°	2418.8	2478.9	2556.8	2604.6	2641.5	2641.5	2666.1	2716.7	2712.6	2711.2	2719.4
20°	2491.2	2559.5	2632.0	2712.6	2742.7	2748.1	2782.3	2808.3	2812.4	2812.4	2812.4
22.5°	2545.9	2626.5	2704.4	2761.8	2785.0	2804.2	2834.2	2850.6	2856.1	2853.4	2856.1
25°	2573.2	2649.7	2729.0	2780.9	2794.6	2805.5	2808.3	2817.8	2816.5	2800.1	2809.6
27.5°	2578.7	2652.5	2704.4	2718.1	2711.2	2704.4	2660.7	2664.8	2652.5	2627.9	2637.4
30°	2554.1	2593.7	2592.3	2550.0	2537.7	2509.0	2469.4	2410.6	2362.8	2342.3	2349.1
32.5°	2465.3	2465.3	2416.1	2320.4	2278.0	2226.1	2155.0	2101.8	2038.9	2025.2	2051.2
35°	2342.3	2272.6	2182.4	2056.7	1992.4	1954.2	1831.2	1792.9	1739.6	1724.6	1736.9
37.5°	2150.9	2034.8	1903.6	1786.1	1731.4	1663.1	1555.1	1500.5	1462.2	1436.2	1448.5
40°	1936.4	1795.6	1659.0	1514.1	1454.0	1398.0	1317.4	1268.2	1206.7	1209.4	1213.5
42.5°	1731.4	1566.1	1413.0	1279.1	1221.7	1175.2	1119.2	1059.1	1037.2	1030.4	1023.5
45°	1514.1	1337.9	1194.4	1094.6	1042.7	998.9	947.0	912.9	886.9	881.4	888.3
47.5°	1309.2	1160.2	1023.5	930.6	888.3	866.4	825.4	794.0	777.6	763.9	772.1
50°	1123.3	983.9	874.6	796.7	766.6	751.6	713.3	696.9	680.5	676.4	675.1
52.5°	970.2	851.4	757.1	694.2	671.0	662.8	634.1	610.8	597.2	601.3	604.0
55°	830.9	729.7	655.9	605.4	586.2	576.7	556.2	539.8	530.2	526.1	528.9
57.5°	707.9	620.4	567.1	526.1	511.1	507.0	485.1	479.7	472.8	468.7	468.7
60°	595.8	534.3	485.1	461.9	445.5	441.4	425.0	418.2	416.8	412.7	410.0
62.5°	501.5	451.0	416.8	392.2	385.4	384.0	373.1	364.9	360.8	358.0	358.0
65°	419.5	382.6	353.9	336.2	330.7	328.0	315.7	312.9	310.2	307.5	306.1
67.5°	349.8	317.0	296.5	284.2	277.4	278.8	271.9	266.5	266.5	265.1	263.7
70°	282.9	262.4	244.6	237.8	235.0	232.3	229.6	225.5	224.1	224.1	224.1
72.5°	222.7	209.1	199.5	195.4	192.7	190.0	187.2	187.2	187.2	185.9	185.9
75°	170.8	165.4	158.5	154.4	154.4	157.2	153.1	149.0	144.9	142.1	143.5
77.5°	128.5	125.7	121.6	114.8	116.2	113.4	113.4	110.7	112.1	112.1	109.3
80°	94.3	90.2	88.8	84.7	86.1	84.7	83.4	83.4	80.6	80.6	80.6
82.5°	65.6	61.5	61.5	60.1	58.8	58.8	57.4	57.4	58.8	56.0	56.0
85°	39.6	38.3	38.3	35.5	35.5	35.5	35.5	36.9	35.5	34.2	34.2
87.5°	17.8	19.1	17.8	16.4	16.4	16.4	15.0	15.0	13.7	15.0	15.0
90°	19.6	20.8	21.9	23.1	23.1	23.1	24.2	25.4	24.2	24.2	24.2
92.5°	376.4	278.3	207.8	164.0	149.6	135.1	117.8	109.7	105.1	105.1	105.1
95°	967.6	855.6	676.7	521.9	465.9	409.9	353.3	317.5	296.8	281.7	296.8
97.5°	1213.6	1232.1	1143.2	1016.1	951.4	886.8	808.3	739.0	704.4	676.7	704.4
100°	1224.0	1392.6	1415.7	1359.1	1316.4	1273.6	1173.2	1102.7	1068.1	1058.9	1068.1
102.5°	1137.4	1384.5	1521.9	1556.5	1545.0	1533.4	1481.5	1435.3	1398.3	1391.4	1398.3
105°	1028.8	1293.3	1493.0	1607.3	1631.0	1654.7	1657.0	1647.8	1631.6	1624.7	1631.6
107.5°	939.9	1181.3	1397.2	1556.5	1605.0	1653.5	1704.3	1725.1	1734.4	1735.5	1734.4
110°	876.4	1082.0	1281.7	1449.2	1512.7	1576.2	1658.2	1706.7	1727.4	1737.8	1727.4

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	840.6	1009.2	1180.1	1336.0	1399.5	1463.0	1558.8	1620.0	1651.2	1669.7	1651.2
115°	821.0	965.3	1107.4	1242.5	1297.9	1353.3	1444.5	1513.8	1550.8	1560.0	1550.8
117.5°	810.6	939.9	1060.0	1169.7	1218.2	1266.7	1347.5	1407.6	1446.8	1452.6	1446.8
120°	802.5	923.8	1031.1	1123.5	1164.5	1205.5	1271.3	1322.1	1352.2	1364.9	1352.2
122.5°	793.3	909.9	1012.7	1094.7	1129.3	1163.9	1217.1	1258.6	1282.9	1295.6	1282.9
125°	782.9	893.7	993.0	1072.7	1104.4	1136.2	1182.4	1215.9	1237.8	1244.8	1237.8
127.5°	769.0	875.3	971.1	1050.8	1080.8	1110.8	1157.0	1187.0	1205.5	1212.4	1205.5
130°	756.3	852.2	943.4	1021.9	1052.5	1083.1	1130.5	1159.3	1177.8	1184.7	1177.8
132.5°	744.8	827.9	912.2	988.4	1019.0	1049.6	1095.8	1129.3	1146.6	1153.5	1146.6
135°	733.2	806.0	881.0	951.5	980.4	1009.2	1055.4	1087.7	1106.2	1113.1	1106.2
137.5°	722.8	785.2	851.0	912.2	938.8	965.3	1009.2	1042.7	1057.7	1065.8	1057.7
140°	714.8	767.9	822.1	874.1	898.4	922.6	963.0	988.4	1004.6	1013.8	1004.6
142.5°	707.8	751.7	797.9	840.6	860.8	881.0	915.7	938.8	952.6	958.4	952.6
145°	699.8	736.7	776.0	810.6	826.8	842.9	871.8	891.4	903.0	908.8	903.0
147.5°	692.8	724.0	756.3	785.2	798.5	811.8	833.7	851.0	860.3	862.6	860.3
150°	684.7	712.5	739.0	762.1	772.5	782.9	801.4	816.4	823.3	824.5	823.3
152.5°	675.5	699.8	721.7	742.5	750.6	758.6	773.7	785.2	788.7	789.8	788.7
155°	666.3	687.0	705.5	722.8	729.8	736.7	748.2	757.5	760.9	760.9	760.9
157.5°	657.0	673.2	689.4	704.4	710.2	715.9	725.2	732.1	734.4	734.4	734.4
160°	646.6	660.5	673.2	685.9	690.5	695.1	702.1	709.0	710.1	710.1	710.1
162.5°	637.4	647.8	658.2	667.4	671.4	675.5	680.1	687.0	688.2	687.0	688.2
165°	627.0	636.2	643.2	651.3	654.2	657.0	661.6	666.3	665.1	664.0	665.1
167.5°	617.8	624.7	630.5	637.4	639.2	640.9	643.2	646.6	646.6	645.5	646.6
170°	608.5	614.3	617.8	622.4	624.1	625.8	628.2	629.3	628.2	628.2	628.2
172.5°	600.4	605.1	607.4	609.7	610.8	612.0	613.1	614.3	613.1	610.8	613.1
175°	594.7	597.0	598.1	600.4	600.4	600.4	600.4	602.8	600.4	598.1	600.4
177.5°	590.1	591.2	592.4	592.4	593.0	593.5	592.4	593.5	591.2	588.9	591.2
180°	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9
2.5°	1823.0	1813.4	1812.0	1812.0	1797.0	1805.2	1788.8	1771.0	1762.8	1762.8	1747.8
5°	1974.7	1965.1	1955.5	1940.5	1940.5	1932.3	1906.3	1880.4	1861.2	1844.8	1827.1
7.5°	2130.4	2120.9	2093.6	2078.5	2086.7	2070.3	2036.2	1992.4	1959.6	1933.7	1896.8
10°	2299.9	2273.9	2260.3	2252.1	2223.4	2205.6	2166.0	2101.8	2060.8	2026.6	1978.8
12.5°	2437.9	2446.1	2394.2	2398.3	2369.6	2345.0	2283.5	2222.0	2160.5	2112.7	2041.6
15°	2586.9	2562.3	2530.8	2506.2	2496.7	2466.6	2414.7	2332.7	2265.7	2190.6	2109.9
17.5°	2704.4	2685.3	2655.2	2632.0	2611.5	2539.0	2495.3	2422.9	2331.3	2257.5	2159.1
20°	2804.2	2786.4	2744.0	2729.0	2692.1	2640.2	2577.3	2465.3	2383.3	2302.6	2207.0
22.5°	2846.5	2828.8	2791.9	2772.7	2749.5	2698.9	2638.8	2532.2	2431.1	2330.0	2228.8
25°	2811.0	2811.0	2793.2	2786.4	2765.9	2720.8	2659.3	2569.1	2461.2	2351.8	2231.6
27.5°	2638.8	2673.0	2685.3	2692.1	2692.1	2693.5	2651.1	2563.6	2458.4	2351.8	2226.1
30°	2390.1	2447.5	2498.0	2513.1	2539.0	2567.7	2585.5	2543.1	2448.9	2336.8	2211.1
32.5°	2077.2	2150.9	2245.2	2268.5	2304.0	2390.1	2437.9	2455.7	2403.8	2305.4	2171.4
35°	1765.6	1858.5	1915.9	1987.0	2019.8	2146.8	2253.4	2317.7	2305.4	2246.6	2125.0
37.5°	1493.6	1546.9	1616.6	1691.8	1757.4	1879.0	2011.6	2135.9	2186.5	2157.8	2066.2
40°	1232.6	1295.5	1378.8	1440.3	1485.4	1607.1	1771.0	1906.3	2017.0	2034.8	1978.8
42.5°	1048.1	1111.0	1161.6	1228.5	1264.1	1381.6	1526.4	1695.9	1827.1	1896.8	1872.2
45°	906.0	944.3	985.3	1023.5	1067.3	1171.1	1305.1	1490.9	1638.5	1736.9	1746.4
47.5°	781.7	815.8	851.4	886.9	911.5	992.1	1115.1	1266.8	1428.0	1563.3	1616.6
50°	694.2	710.6	736.6	757.1	785.8	855.5	953.9	1085.0	1255.9	1402.1	1471.8
52.5°	608.1	628.6	649.1	666.9	686.0	735.2	825.4	938.8	1086.4	1236.7	1322.8
55°	535.7	552.1	571.2	583.5	594.4	638.2	706.5	794.0	921.1	1063.2	1169.8
57.5°	476.9	483.8	500.2	507.0	519.3	554.8	604.0	681.9	784.4	922.4	1009.9
60°	412.7	426.4	438.7	444.1	453.7	478.3	512.5	584.9	673.7	774.8	874.6
62.5°	360.8	366.2	375.8	382.6	389.5	415.4	444.1	498.8	565.8	650.5	742.0
65°	312.9	315.7	321.1	330.7	334.8	353.9	370.3	410.0	472.8	537.1	628.6
67.5°	263.7	266.5	273.3	278.8	282.9	295.2	312.9	341.6	375.8	446.9	497.4
70°	225.5	225.5	229.6	232.3	236.4	241.9	251.4	273.3	304.7	349.8	396.3
72.5°	188.6	188.6	188.6	192.7	192.7	196.8	202.2	217.3	239.1	274.7	304.7
75°	146.2	147.6	150.3	150.3	151.7	157.2	161.3	165.4	176.3	199.5	226.8
77.5°	110.7	113.4	114.8	112.1	114.8	114.8	120.3	125.7	131.2	138.0	158.5
80°	82.0	83.4	80.6	82.0	82.0	84.7	87.5	86.1	88.8	97.0	102.5
82.5°	54.7	56.0	56.0	56.0	56.0	60.1	60.1	58.8	60.1	61.5	62.9
85°	34.2	32.8	32.8	34.2	32.8	32.8	34.2	35.5	34.2	35.5	36.9
87.5°	15.0	15.0	15.0	15.0	13.7	13.7	15.0	13.7	15.0	13.7	12.3
90°	25.4	24.2	23.1	23.1	23.1	21.9	20.8	19.6	20.8	18.5	16.2
92.5°	109.7	117.8	135.1	149.6	164.0	207.8	278.3	376.4	452.6	396.1	287.5
95°	317.5	353.3	409.9	465.9	521.9	676.7	855.6	967.6	941.1	710.1	434.2
97.5°	739.0	808.3	886.8	951.4	1016.1	1143.2	1232.1	1213.6	1006.9	680.1	396.1
100°	1102.7	1173.2	1273.6	1316.4	1359.1	1415.7	1392.6	1224.0	928.4	602.8	367.2
102.5°	1435.3	1481.5	1533.4	1545.0	1556.5	1521.9	1384.5	1137.4	830.2	550.8	359.1
105°	1647.8	1657.0	1654.7	1631.0	1607.3	1493.0	1293.3	1028.8	757.5	525.4	363.7
107.5°	1725.1	1704.3	1653.5	1605.0	1556.5	1397.2	1181.3	939.9	710.1	518.5	377.6
110°	1706.7	1658.2	1576.2	1512.7	1449.2	1281.7	1082.0	876.4	688.2	520.8	393.8

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1620.0	1558.8	1463.0	1399.5	1336.0	1180.1	1009.2	840.6	677.8	527.7	411.1
115°	1513.8	1444.5	1353.3	1297.9	1242.5	1107.4	965.3	821.0	675.5	536.9	429.5
117.5°	1407.6	1347.5	1266.7	1218.2	1169.7	1060.0	939.9	810.6	674.3	546.2	448.0
120°	1322.1	1271.3	1205.5	1164.5	1123.5	1031.1	923.8	802.5	674.3	556.6	467.7
122.5°	1258.6	1217.1	1163.9	1129.3	1094.7	1012.7	909.9	793.3	673.2	567.0	486.1
125°	1215.9	1182.4	1136.2	1104.4	1072.7	993.0	893.7	782.9	672.0	577.4	504.6
127.5°	1187.0	1157.0	1110.8	1080.8	1050.8	971.1	875.3	769.0	669.7	585.4	520.8
130°	1159.3	1130.5	1083.1	1052.5	1021.9	943.4	852.2	756.3	668.6	594.7	535.8
132.5°	1129.3	1095.8	1049.6	1019.0	988.4	912.2	827.9	744.8	667.4	602.8	550.8
135°	1087.7	1055.4	1009.2	980.4	951.5	881.0	806.0	733.2	666.3	610.8	563.5
137.5°	1042.7	1009.2	965.3	938.8	912.2	851.0	785.2	722.8	666.3	615.5	572.7
140°	988.4	963.0	922.6	898.4	874.1	822.1	767.9	714.8	665.1	621.2	582.0
142.5°	938.8	915.7	881.0	860.8	840.6	797.9	751.7	707.8	665.1	625.8	588.9
145°	891.4	871.8	842.9	826.8	810.6	776.0	736.7	699.8	662.8	627.0	593.5
147.5°	851.0	833.7	811.8	798.5	785.2	756.3	724.0	692.8	659.3	628.2	598.1
150°	816.4	801.4	782.9	772.5	762.1	739.0	712.5	684.7	655.9	628.2	601.6
152.5°	785.2	773.7	758.6	750.6	742.5	721.7	699.8	675.5	650.1	625.8	603.9
155°	757.5	748.2	736.7	729.8	722.8	705.5	687.0	666.3	644.3	623.5	605.1
157.5°	732.1	725.2	715.9	710.2	704.4	689.4	673.2	657.0	638.6	621.2	605.1
160°	709.0	702.1	695.1	690.5	685.9	673.2	660.5	646.6	631.6	617.8	605.1
162.5°	687.0	680.1	675.5	671.4	667.4	658.2	647.8	637.4	624.7	614.3	605.1
165°	666.3	661.6	657.0	654.2	651.3	643.2	636.2	627.0	617.8	609.7	602.8
167.5°	646.6	643.2	640.9	639.2	637.4	630.5	624.7	617.8	610.8	605.1	600.4
170°	629.3	628.2	625.8	624.1	622.4	617.8	614.3	608.5	603.9	600.4	598.1
172.5°	614.3	613.1	612.0	610.8	609.7	607.4	605.1	600.4	597.0	595.8	595.8
175°	602.8	600.4	600.4	600.4	600.4	598.1	597.0	594.7	592.4	592.4	593.5
177.5°	593.5	592.4	593.5	593.0	592.4	592.4	591.2	590.1	588.9	588.9	591.2
180°	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9
2.5°	1739.6	1732.8	1728.7	1727.3	1715.0	1708.2	1704.1	1701.4	1697.3	1686.3	1676.8
5°	1805.2	1786.1	1776.5	1765.6	1746.4	1724.6	1706.8	1695.9	1682.2	1660.4	1639.9
7.5°	1866.7	1838.0	1818.9	1803.8	1771.0	1735.5	1706.8	1683.6	1657.6	1627.6	1598.9
10°	1930.9	1884.5	1859.9	1836.6	1788.8	1742.3	1701.4	1667.2	1630.3	1590.7	1559.2
12.5°	1981.5	1920.0	1892.7	1859.9	1801.1	1746.4	1694.5	1648.1	1600.2	1557.9	1512.8
15°	2040.3	1963.7	1932.3	1889.9	1809.3	1738.2	1671.3	1620.7	1571.5	1508.7	1460.8
17.5°	2074.4	1985.6	1940.5	1903.6	1816.1	1730.0	1652.2	1589.3	1531.9	1469.0	1418.5
20°	2108.6	2007.5	1956.9	1905.0	1801.1	1709.6	1627.6	1552.4	1492.3	1423.9	1372.0
22.5°	2119.5	2002.0	1948.7	1900.9	1791.5	1689.1	1594.8	1518.2	1448.5	1380.2	1321.5
25°	2119.5	2000.6	1937.8	1876.3	1761.5	1656.3	1562.0	1478.6	1400.7	1332.4	1273.6
27.5°	2097.7	1973.3	1907.7	1851.7	1732.8	1619.4	1522.3	1430.8	1355.6	1287.3	1220.3
30°	2070.3	1933.7	1868.1	1801.1	1686.3	1578.4	1473.1	1388.4	1309.2	1231.3	1171.1
32.5°	2036.2	1891.3	1818.9	1750.5	1628.9	1516.9	1419.8	1336.5	1261.3	1180.7	1113.7
35°	1987.0	1828.4	1747.8	1687.7	1570.2	1454.0	1361.1	1279.1	1206.7	1123.3	1050.9
37.5°	1924.1	1771.0	1689.1	1615.3	1493.6	1387.0	1299.6	1220.3	1149.3	1072.7	992.1
40°	1850.3	1690.4	1619.4	1541.5	1413.0	1311.9	1229.9	1158.8	1087.8	1015.3	937.5
42.5°	1766.9	1608.4	1529.2	1454.0	1331.0	1231.3	1154.7	1090.5	1024.9	957.9	874.6
45°	1667.2	1518.2	1441.7	1370.6	1251.8	1149.3	1079.6	1018.1	962.0	893.7	819.9
47.5°	1555.1	1425.3	1347.4	1270.9	1154.7	1065.9	997.6	945.7	897.8	829.5	762.5
50°	1445.8	1317.4	1254.5	1176.6	1070.0	986.6	917.0	873.2	836.3	769.4	709.2
52.5°	1307.8	1210.8	1150.6	1083.7	981.2	896.5	841.8	803.5	759.8	707.9	654.6
55°	1186.2	1096.0	1048.1	985.3	884.2	809.0	762.5	727.0	692.8	646.4	604.0
57.5°	1048.1	992.1	944.3	889.6	789.9	725.6	684.6	654.6	623.1	584.9	550.7
60°	903.3	877.3	830.9	787.1	702.4	646.4	612.2	584.9	554.8	523.4	494.7
62.5°	774.8	759.8	732.5	698.3	619.0	571.2	537.1	516.6	494.7	466.0	438.7
65°	653.2	646.4	620.4	595.8	541.2	498.8	468.7	456.4	431.8	410.0	385.4
67.5°	545.3	537.1	522.0	511.1	464.6	425.0	410.0	393.6	373.1	356.7	336.2
70°	435.9	434.6	425.0	411.3	386.7	358.0	343.0	332.1	311.6	299.3	284.2
72.5°	338.9	345.7	337.5	332.1	315.7	295.2	281.5	274.7	258.3	248.7	237.8
75°	252.8	258.3	262.4	252.8	248.7	239.1	226.8	220.0	211.8	198.1	194.0
77.5°	172.2	184.5	184.5	187.2	188.6	183.1	173.6	168.1	158.5	155.8	150.3
80°	113.4	124.4	125.7	128.5	132.6	132.6	125.7	124.4	114.8	113.4	109.3
82.5°	65.6	75.2	80.6	84.7	83.4	88.8	83.4	82.0	76.5	76.5	73.8
85°	35.5	36.9	39.6	42.4	45.1	47.8	47.8	46.5	45.1	43.7	41.0
87.5°	13.7	13.7	15.0	13.7	15.0	17.8	19.1	19.1	17.8	16.4	13.7
90°	16.2	9.2	9.2	9.2	8.1	6.9	3.5	1.2	3.5	6.9	8.1
92.5°	175.5	103.9	88.9	73.9	53.1	35.8	23.1	16.2	23.1	35.8	53.1
95°	244.8	144.3	120.0	95.8	68.1	53.1	41.6	38.1	41.6	53.1	68.1
97.5°	233.3	153.6	132.8	112.0	87.8	73.9	63.5	63.5	63.5	73.9	87.8
100°	236.7	168.6	150.1	131.6	109.7	95.8	87.8	87.8	87.8	95.8	109.7
102.5°	248.3	188.2	170.9	153.6	132.8	120.1	113.2	110.9	113.2	120.1	132.8
105°	267.9	212.5	195.8	179.0	158.2	144.3	138.6	135.1	138.6	144.3	158.2
107.5°	288.7	237.9	221.2	204.4	184.8	169.7	164.0	161.7	164.0	169.7	184.8
110°	312.9	262.1	246.5	230.9	210.2	196.3	190.5	188.2	190.5	196.3	210.2

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	336.0	287.5	271.9	256.3	235.6	222.9	215.9	213.6	215.9	222.9	235.6
115°	360.3	314.1	298.5	282.9	261.0	249.4	241.3	237.9	241.3	249.4	261.0
117.5°	383.4	339.5	323.4	307.2	286.4	273.7	266.7	263.3	266.7	273.7	286.4
120°	407.6	363.7	347.5	331.4	311.8	299.1	291.0	288.7	291.0	299.1	311.8
122.5°	430.7	386.8	371.2	355.6	333.7	322.2	314.1	311.8	314.1	322.2	333.7
125°	451.5	409.9	393.8	377.6	355.6	342.9	336.0	331.4	336.0	342.9	355.6
127.5°	471.1	430.7	414.6	398.4	375.3	361.4	353.3	349.9	353.3	361.4	375.3
130°	490.7	451.5	434.8	418.0	396.1	378.7	369.5	364.9	369.5	378.7	396.1
132.5°	506.9	467.7	452.1	436.5	412.2	396.1	383.4	379.9	383.4	396.1	412.2
135°	521.9	483.8	468.8	453.8	429.5	409.9	398.4	393.8	398.4	409.9	429.5
137.5°	533.5	497.7	483.2	468.8	443.4	424.9	412.2	407.6	412.2	424.9	443.4
140°	545.0	510.4	496.6	482.7	458.4	438.8	426.1	422.6	426.1	438.8	458.4
142.5°	555.4	521.9	508.6	495.4	472.3	453.8	442.3	438.8	442.3	453.8	472.3
145°	562.3	532.3	519.6	506.9	485.0	468.8	457.3	453.8	457.3	468.8	485.0
147.5°	570.4	541.6	530.0	518.5	500.0	482.7	472.3	471.1	472.3	482.7	500.0
150°	576.2	550.8	539.8	528.9	511.5	497.7	488.4	487.3	488.4	497.7	511.5
152.5°	580.8	558.9	549.0	539.2	524.2	511.5	502.3	502.3	502.3	511.5	524.2
155°	585.4	565.8	557.2	548.5	535.8	524.2	517.3	516.2	517.3	524.2	535.8
157.5°	588.9	571.6	564.7	557.7	546.2	536.9	530.0	530.0	530.0	536.9	546.2
160°	591.2	577.4	571.0	564.6	555.4	547.3	542.7	542.7	542.7	547.3	555.4
162.5°	593.5	580.8	576.2	571.6	563.5	556.6	553.1	554.3	553.1	556.6	563.5
165°	593.5	583.1	579.7	576.2	570.4	564.6	562.3	562.3	562.3	564.6	570.4
167.5°	593.5	585.4	582.6	579.7	576.2	571.6	570.4	571.6	570.4	571.6	576.2
170°	592.4	586.6	584.8	583.1	580.8	577.4	576.2	577.4	576.2	577.4	580.8
172.5°	591.2	587.7	586.6	585.4	584.3	582.0	582.0	583.1	582.0	582.0	584.3
175°	590.1	587.7	587.7	587.7	586.6	585.4	585.4	586.6	585.4	585.4	586.6
177.5°	588.9	587.7	587.7	587.7	587.7	586.6	587.7	588.9	587.7	586.6	587.7
180°	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9
2.5°	1668.6	1665.8	1663.1	1652.2	1642.6	1626.2	1612.5	1607.1	1605.7	1607.1	1603.0
5°	1620.7	1619.4	1609.8	1590.7	1572.9	1553.8	1540.1	1526.4	1518.2	1518.2	1508.7
7.5°	1575.6	1566.1	1557.9	1533.3	1512.8	1486.8	1466.3	1454.0	1447.2	1432.1	1432.1
10°	1527.8	1514.1	1503.2	1480.0	1449.9	1423.9	1398.0	1382.9	1370.6	1359.7	1355.6
12.5°	1480.0	1469.0	1448.5	1423.9	1393.9	1361.1	1333.8	1322.8	1294.1	1270.9	1272.3
15°	1434.9	1410.3	1400.7	1365.2	1329.7	1298.2	1258.6	1227.2	1203.9	1188.9	1169.8
17.5°	1384.3	1359.7	1341.9	1311.9	1265.4	1216.2	1178.0	1135.6	1112.4	1086.4	1074.1
20°	1328.3	1307.8	1294.1	1246.3	1190.3	1131.5	1089.1	1063.2	1037.2	1018.1	1007.1
22.5°	1280.5	1254.5	1238.1	1173.9	1112.4	1053.6	1020.8	998.9	977.1	960.7	955.2
25°	1219.0	1203.9	1164.3	1108.3	1033.1	993.5	964.8	936.1	923.8	912.9	900.6
27.5°	1168.4	1131.5	1104.2	1030.4	983.9	938.8	910.1	888.3	873.2	862.3	852.7
30°	1105.5	1071.4	1033.1	971.6	929.3	886.9	860.9	843.2	826.8	819.9	811.7
32.5°	1039.9	1008.5	971.6	922.4	870.5	837.7	817.2	798.1	787.1	780.3	770.7
35°	981.2	941.6	917.0	870.5	828.1	791.2	772.1	755.7	743.4	740.7	739.3
37.5°	918.3	888.3	865.0	817.2	781.7	750.2	732.5	714.7	707.9	706.5	701.0
40°	863.7	837.7	815.8	770.7	732.5	703.8	690.1	679.2	672.3	672.3	671.0
42.5°	815.8	788.5	766.6	725.6	691.5	665.5	650.5	639.5	636.8	638.2	636.8
45°	762.5	739.3	717.4	675.1	646.4	627.2	610.8	605.4	601.3	602.6	604.0
47.5°	712.0	692.8	671.0	636.8	604.0	583.5	574.0	568.5	568.5	568.5	571.2
50°	666.9	645.0	625.9	590.3	560.3	543.9	535.7	528.9	530.2	531.6	533.0
52.5°	613.6	594.4	580.8	545.3	523.4	502.9	493.3	494.7	493.3	493.3	496.1
55°	567.1	548.0	534.3	501.5	479.7	466.0	457.8	453.7	455.1	452.3	457.8
57.5°	515.2	498.8	489.2	457.8	438.7	426.4	419.5	412.7	415.4	414.1	412.7
60°	470.1	451.0	435.9	414.1	397.7	382.6	378.5	371.7	374.4	371.7	370.3
62.5°	418.2	403.1	392.2	370.3	356.7	344.4	334.8	330.7	329.3	325.2	321.1
65°	366.2	358.0	347.1	325.2	311.6	302.0	296.5	292.4	291.1	280.1	267.8
67.5°	318.4	312.9	302.0	285.6	273.3	263.7	255.5	248.7	240.5	232.3	225.5
70°	273.3	265.1	258.3	243.2	232.3	222.7	214.5	206.3	202.2	194.0	191.3
72.5°	229.6	221.4	214.5	200.9	191.3	181.8	179.0	169.5	165.4	164.0	164.0
75°	184.5	177.7	173.6	161.3	153.1	146.2	142.1	139.4	136.7	133.9	129.8
77.5°	140.8	136.7	133.9	125.7	118.9	114.8	113.4	103.9	101.1	98.4	95.7
80°	102.5	101.1	98.4	91.6	88.8	79.3	79.3	76.5	75.2	75.2	75.2
82.5°	69.7	67.0	65.6	58.8	57.4	56.0	54.7	53.3	54.7	53.3	54.7
85°	36.9	35.5	34.2	34.2	34.2	34.2	34.2	34.2	34.2	32.8	34.2
87.5°	13.7	13.7	13.7	13.7	12.3	13.7	13.7	12.3	13.7	13.7	13.7
90°	9.2	9.2	9.2	16.2	16.2	18.5	20.8	19.6	20.8	21.9	23.1
92.5°	73.9	88.9	103.9	175.5	287.5	396.1	452.6	376.4	278.3	207.8	164.0
95°	95.8	120.0	144.3	244.8	434.2	710.1	941.1	967.6	855.6	676.7	521.9
97.5°	112.0	132.8	153.6	233.3	396.1	680.1	1006.9	1213.6	1232.1	1143.2	1016.1
100°	131.6	150.1	168.6	236.7	367.2	602.8	928.4	1224.0	1392.6	1415.7	1359.1
102.5°	153.6	170.9	188.2	248.3	359.1	550.8	830.2	1137.4	1384.5	1521.9	1556.5
105°	179.0	195.8	212.5	267.9	363.7	525.4	757.5	1028.8	1293.3	1493.0	1607.3
107.5°	204.4	221.2	237.9	288.7	377.6	518.5	710.1	939.9	1181.3	1397.2	1556.5
110°	230.9	246.5	262.1	312.9	393.8	520.8	688.2	876.4	1082.0	1281.7	1449.2

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	256.3	271.9	287.5	336.0	411.1	527.7	677.8	840.6	1009.2	1180.1	1336.0
115°	282.9	298.5	314.1	360.3	429.5	536.9	675.5	821.0	965.3	1107.4	1242.5
117.5°	307.2	323.4	339.5	383.4	448.0	546.2	674.3	810.6	939.9	1060.0	1169.7
120°	331.4	347.5	363.7	407.6	467.7	556.6	674.3	802.5	923.8	1031.1	1123.5
122.5°	355.6	371.2	386.8	430.7	486.1	567.0	673.2	793.3	909.9	1012.7	1094.7
125°	377.6	393.8	409.9	451.5	504.6	577.4	672.0	782.9	893.7	993.0	1072.7
127.5°	398.4	414.6	430.7	471.1	520.8	585.4	669.7	769.0	875.3	971.1	1050.8
130°	418.0	434.8	451.5	490.7	535.8	594.7	668.6	756.3	852.2	943.4	1021.9
132.5°	436.5	452.1	467.7	506.9	550.8	602.8	667.4	744.8	827.9	912.2	988.4
135°	453.8	468.8	483.8	521.9	563.5	610.8	666.3	733.2	806.0	881.0	951.5
137.5°	468.8	483.2	497.7	533.5	572.7	615.5	666.3	722.8	785.2	851.0	912.2
140°	482.7	496.6	510.4	545.0	582.0	621.2	665.1	714.8	767.9	822.1	874.1
142.5°	495.4	508.6	521.9	555.4	588.9	625.8	665.1	707.8	751.7	797.9	840.6
145°	506.9	519.6	532.3	562.3	593.5	627.0	662.8	699.8	736.7	776.0	810.6
147.5°	518.5	530.0	541.6	570.4	598.1	628.2	659.3	692.8	724.0	756.3	785.2
150°	528.9	539.8	550.8	576.2	601.6	628.2	655.9	684.7	712.5	739.0	762.1
152.5°	539.2	549.0	558.9	580.8	603.9	625.8	650.1	675.5	699.8	721.7	742.5
155°	548.5	557.2	565.8	585.4	605.1	623.5	644.3	666.3	687.0	705.5	722.8
157.5°	557.7	564.7	571.6	588.9	605.1	621.2	638.6	657.0	673.2	689.4	704.4
160°	564.6	571.0	577.4	591.2	605.1	617.8	631.6	646.6	660.5	673.2	685.9
162.5°	571.6	576.2	580.8	593.5	605.1	614.3	624.7	637.4	647.8	658.2	667.4
165°	576.2	579.7	583.1	593.5	602.8	609.7	617.8	627.0	636.2	643.2	651.3
167.5°	579.7	582.6	585.4	593.5	600.4	605.1	610.8	617.8	624.7	630.5	637.4
170°	583.1	584.8	586.6	592.4	598.1	600.4	603.9	608.5	614.3	617.8	622.4
172.5°	585.4	586.6	587.7	591.2	595.8	595.8	597.0	600.4	605.1	607.4	609.7
175°	587.7	587.7	587.7	590.1	593.5	592.4	592.4	594.7	597.0	598.1	600.4
177.5°	587.7	587.7	587.7	588.9	591.2	588.9	588.9	590.1	591.2	592.4	592.4
180°	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9
2.5°	1603.0	1608.4	1601.6	1605.7	1596.1	1594.8	1596.1	1596.1	1597.5	1598.9	1600.2
5°	1512.8	1511.4	1503.2	1497.7	1493.6	1497.7	1500.5	1503.2	1500.5	1503.2	1504.6
7.5°	1428.0	1423.9	1419.8	1410.3	1413.0	1410.3	1418.5	1414.4	1414.4	1421.2	1426.7
10°	1352.9	1344.7	1341.9	1331.0	1322.8	1321.5	1331.0	1335.1	1339.2	1341.9	1352.9
12.5°	1255.9	1243.6	1234.0	1238.1	1214.9	1224.4	1227.2	1221.7	1238.1	1257.2	1246.3
15°	1152.0	1153.4	1134.2	1127.4	1108.3	1113.7	1115.1	1128.8	1142.4	1141.1	1157.5
17.5°	1075.5	1067.3	1050.9	1049.5	1041.3	1045.4	1044.0	1055.0	1050.9	1057.7	1071.4
20°	1004.4	998.9	985.3	979.8	982.5	979.8	981.2	982.5	986.6	1001.7	998.9
22.5°	948.4	941.6	941.6	934.7	926.5	923.8	930.6	934.7	940.2	942.9	949.8
25°	899.2	893.7	886.9	882.8	876.0	877.3	881.4	886.9	891.0	896.5	901.9
27.5°	848.6	848.6	841.8	840.4	837.7	836.3	841.8	844.5	844.5	848.6	854.1
30°	809.0	809.0	802.2	800.8	799.4	799.4	803.5	804.9	806.3	810.4	813.1
32.5°	770.7	769.4	766.6	768.0	766.6	768.0	768.0	769.4	772.1	773.5	778.9
35°	735.2	736.6	733.8	733.8	732.5	733.8	736.6	737.9	739.3	742.0	742.0
37.5°	701.0	703.8	702.4	706.5	706.5	706.5	706.5	709.2	709.2	709.2	707.9
40°	671.0	671.0	669.6	672.3	675.1	675.1	676.4	676.4	677.8	677.8	676.4
42.5°	636.8	639.5	643.6	645.0	647.7	646.4	650.5	649.1	650.5	647.7	645.0
45°	605.4	605.4	610.8	616.3	617.7	617.7	617.7	620.4	617.7	613.6	612.2
47.5°	571.2	574.0	576.7	583.5	584.9	584.9	584.9	584.9	582.1	582.1	582.1
50°	537.1	538.4	539.8	542.5	546.6	545.3	545.3	545.3	550.7	545.3	546.6
52.5°	496.1	497.4	498.8	504.3	502.9	502.9	504.3	504.3	508.4	507.0	504.3
55°	455.1	455.1	457.8	457.8	457.8	460.5	461.9	464.6	463.3	464.6	466.0
57.5°	414.1	411.3	410.0	410.0	414.1	412.7	414.1	414.1	419.5	422.3	423.6
60°	366.2	366.2	364.9	356.7	356.7	355.3	359.4	362.1	364.9	377.2	375.8
62.5°	317.0	311.6	306.1	307.5	299.3	303.4	300.6	303.4	311.6	321.1	322.5
65°	267.8	263.7	258.3	256.9	254.2	258.3	256.9	258.3	262.4	267.8	274.7
67.5°	224.1	222.7	220.0	218.6	218.6	218.6	221.4	221.4	222.7	226.8	230.9
70°	191.3	190.0	191.3	188.6	190.0	188.6	190.0	191.3	192.7	194.0	198.1
72.5°	161.3	161.3	161.3	158.5	161.3	159.9	159.9	161.3	162.6	164.0	166.7
75°	128.5	125.7	123.0	120.3	118.9	121.6	123.0	121.6	125.7	131.2	131.2
77.5°	97.0	95.7	95.7	95.7	97.0	95.7	98.4	97.0	98.4	98.4	101.1
80°	75.2	73.8	75.2	75.2	73.8	76.5	75.2	75.2	76.5	77.9	76.5
82.5°	54.7	56.0	54.7	54.7	54.7	57.4	54.7	54.7	54.7	56.0	56.0
85°	34.2	34.2	34.2	34.2	35.5	34.2	35.5	34.2	36.9	35.5	35.5
87.5°	12.3	13.7	15.0	15.0	15.0	15.0	13.7	15.0	16.4	15.0	16.4
90°	23.1	23.1	24.2	25.4	24.2	24.2	24.2	25.4	24.2	23.1	23.1
92.5°	149.6	135.1	117.8	109.7	105.1	105.1	105.1	109.7	117.8	135.1	149.6
95°	465.9	409.9	353.3	317.5	296.8	281.7	296.8	317.5	353.3	409.9	465.9
97.5°	951.4	886.8	808.3	739.0	704.4	676.7	704.4	739.0	808.3	886.8	951.4
100°	1316.4	1273.6	1173.2	1102.7	1068.1	1058.9	1068.1	1102.7	1173.2	1273.6	1316.4
102.5°	1545.0	1533.4	1481.5	1435.3	1398.3	1391.4	1398.3	1435.3	1481.5	1533.4	1545.0
105°	1631.0	1654.7	1657.0	1647.8	1631.6	1624.7	1631.6	1647.8	1657.0	1654.7	1631.0
107.5°	1605.0	1653.5	1704.3	1725.1	1734.4	1735.5	1734.4	1725.1	1704.3	1653.5	1605.0
110°	1512.7	1576.2	1658.2	1706.7	1727.4	1737.8	1727.4	1706.7	1658.2	1576.2	1512.7

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1399.5	1463.0	1558.8	1620.0	1651.2	1669.7	1651.2	1620.0	1558.8	1463.0	1399.5
115°	1297.9	1353.3	1444.5	1513.8	1550.8	1560.0	1550.8	1513.8	1444.5	1353.3	1297.9
117.5°	1218.2	1266.7	1347.5	1407.6	1446.8	1452.6	1446.8	1407.6	1347.5	1266.7	1218.2
120°	1164.5	1205.5	1271.3	1322.1	1352.2	1364.9	1352.2	1322.1	1271.3	1205.5	1164.5
122.5°	1129.3	1163.9	1217.1	1258.6	1282.9	1295.6	1282.9	1258.6	1217.1	1163.9	1129.3
125°	1104.4	1136.2	1182.4	1215.9	1237.8	1244.8	1237.8	1215.9	1182.4	1136.2	1104.4
127.5°	1080.8	1110.8	1157.0	1187.0	1205.5	1212.4	1205.5	1187.0	1157.0	1110.8	1080.8
130°	1052.5	1083.1	1130.5	1159.3	1177.8	1184.7	1177.8	1159.3	1130.5	1083.1	1052.5
132.5°	1019.0	1049.6	1095.8	1129.3	1146.6	1153.5	1146.6	1129.3	1095.8	1049.6	1019.0
135°	980.4	1009.2	1055.4	1087.7	1106.2	1113.1	1106.2	1087.7	1055.4	1009.2	980.4
137.5°	938.8	965.3	1009.2	1042.7	1057.7	1065.8	1057.7	1042.7	1009.2	965.3	938.8
140°	898.4	922.6	963.0	988.4	1004.6	1013.8	1004.6	988.4	963.0	922.6	898.4
142.5°	860.8	881.0	915.7	938.8	952.6	958.4	952.6	938.8	915.7	881.0	860.8
145°	826.8	842.9	871.8	891.4	903.0	908.8	903.0	891.4	871.8	842.9	826.8
147.5°	798.5	811.8	833.7	851.0	860.3	862.6	860.3	851.0	833.7	811.8	798.5
150°	772.5	782.9	801.4	816.4	823.3	824.5	823.3	816.4	801.4	782.9	772.5
152.5°	750.6	758.6	773.7	785.2	788.7	789.8	788.7	785.2	773.7	758.6	750.6
155°	729.8	736.7	748.2	757.5	760.9	760.9	760.9	757.5	748.2	736.7	729.8
157.5°	710.2	715.9	725.2	732.1	734.4	734.4	734.4	732.1	725.2	715.9	710.2
160°	690.5	695.1	702.1	709.0	710.1	710.1	710.1	709.0	702.1	695.1	690.5
162.5°	671.4	675.5	680.1	687.0	688.2	687.0	688.2	687.0	680.1	675.5	671.4
165°	654.2	657.0	661.6	666.3	665.1	664.0	665.1	666.3	661.6	657.0	654.2
167.5°	639.2	640.9	643.2	646.6	646.6	645.5	646.6	646.6	643.2	640.9	639.2
170°	624.1	625.8	628.2	629.3	628.2	628.2	628.2	629.3	628.2	625.8	624.1
172.5°	610.8	612.0	613.1	614.3	613.1	610.8	613.1	614.3	613.1	612.0	610.8
175°	600.4	600.4	600.4	602.8	600.4	598.1	600.4	602.8	600.4	600.4	600.4
177.5°	593.0	593.5	592.4	593.5	591.2	588.9	591.2	593.5	592.4	593.5	593.0
180°	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9	1695.9
2.5°	1605.7	1612.5	1609.8	1600.2	1604.3	1612.5	1620.7	1631.7	1638.5	1644.0	1646.7
5°	1511.4	1523.7	1521.0	1521.0	1526.4	1540.1	1553.8	1577.0	1585.2	1594.8	1608.4
7.5°	1428.0	1437.6	1445.8	1448.5	1456.7	1474.5	1492.3	1518.2	1538.7	1549.7	1557.9
10°	1354.2	1361.1	1373.4	1380.2	1388.4	1410.3	1436.2	1463.6	1484.1	1503.2	1514.1
12.5°	1260.0	1287.3	1303.7	1314.6	1325.6	1358.3	1378.8	1408.9	1433.5	1451.3	1467.7
15°	1154.7	1187.5	1197.1	1239.5	1266.8	1292.8	1324.2	1359.7	1382.9	1403.4	1425.3
17.5°	1065.9	1089.1	1100.1	1145.2	1168.4	1209.4	1254.5	1299.6	1335.1	1350.1	1372.0
20°	1009.9	1022.2	1044.0	1059.1	1083.7	1131.5	1180.7	1235.4	1288.7	1303.7	1325.6
22.5°	952.5	968.9	983.9	1004.4	1023.5	1056.3	1105.5	1165.7	1223.1	1250.4	1276.4
25°	900.6	917.0	926.5	948.4	966.1	998.9	1033.1	1094.6	1162.9	1186.2	1227.2
27.5°	859.6	869.1	885.5	895.1	915.6	945.7	977.1	1023.5	1090.5	1130.1	1169.8
30°	818.6	825.4	839.1	852.7	867.8	888.3	923.8	968.9	1030.4	1064.5	1104.2
32.5°	777.6	788.5	796.7	806.3	822.7	847.3	871.9	915.6	964.8	1003.0	1042.7
35°	743.4	747.5	758.4	769.4	780.3	802.2	828.1	870.5	914.2	944.3	979.8
37.5°	706.5	713.3	721.5	725.6	743.4	757.1	784.4	817.2	869.1	888.3	923.8
40°	677.8	676.4	684.6	691.5	699.7	721.5	737.9	773.5	814.5	844.5	866.4
42.5°	642.3	642.3	645.0	653.2	664.1	677.8	696.9	727.0	769.4	791.2	817.2
45°	613.6	609.5	610.8	616.3	623.1	636.8	655.9	681.9	724.3	742.0	769.4
47.5°	579.4	575.3	575.3	580.8	586.2	595.8	610.8	640.9	675.1	698.3	718.8
50°	541.2	542.5	541.2	545.3	548.0	557.6	574.0	598.5	630.0	649.1	672.3
52.5°	505.6	502.9	501.5	504.3	509.7	516.6	534.3	556.2	586.2	605.4	625.9
55°	461.9	464.6	464.6	464.6	472.8	475.6	489.2	511.1	541.2	556.2	575.3
57.5°	422.3	420.9	423.6	422.3	429.1	438.7	449.6	466.0	496.1	511.1	528.9
60°	378.5	379.9	381.3	381.3	386.7	396.3	408.6	423.6	448.2	463.3	479.7
62.5°	325.2	332.1	338.9	341.6	349.8	356.7	364.9	381.3	403.1	414.1	429.1
65°	274.7	284.2	293.8	300.6	306.1	312.9	323.9	338.9	356.7	367.6	382.6
67.5°	230.9	237.8	250.1	256.9	267.8	276.0	282.9	295.2	317.0	321.1	333.4
70°	199.5	202.2	207.7	213.2	225.5	232.3	240.5	252.8	269.2	278.8	285.6
72.5°	168.1	169.5	172.2	177.7	183.1	191.3	200.9	211.8	226.8	230.9	240.5
75°	133.9	142.1	142.1	146.2	150.3	154.4	162.6	173.6	183.1	190.0	195.4
77.5°	99.8	103.9	106.6	113.4	118.9	123.0	128.5	136.7	142.1	147.6	151.7
80°	77.9	79.3	80.6	80.6	83.4	88.8	94.3	99.8	106.6	109.3	113.4
82.5°	57.4	57.4	57.4	60.1	61.5	62.9	62.9	65.6	72.4	75.2	79.3
85°	36.9	36.9	36.9	36.9	38.3	39.6	41.0	42.4	42.4	42.4	45.1
87.5°	15.0	17.8	16.4	17.8	17.8	17.8	17.8	19.1	19.1	20.5	20.5
90°	23.1	21.9	20.8	19.6	20.8	18.5	16.2	16.2	9.2	9.2	9.2
92.5°	164.0	207.8	278.3	376.4	452.6	396.1	287.5	175.5	103.9	88.9	73.9
95°	521.9	676.7	855.6	967.6	941.1	710.1	434.2	244.8	144.3	120.0	95.8
97.5°	1016.1	1143.2	1232.1	1213.6	1006.9	680.1	396.1	233.3	153.6	132.8	112.0
100°	1359.1	1415.7	1392.6	1224.0	928.4	602.8	367.2	236.7	168.6	150.1	131.6
102.5°	1556.5	1521.9	1384.5	1137.4	830.2	550.8	359.1	248.3	188.2	170.9	153.6
105°	1607.3	1493.0	1293.3	1028.8	757.5	525.4	363.7	267.9	212.5	195.8	179.0
107.5°	1556.5	1397.2	1181.3	939.9	710.1	518.5	377.6	288.7	237.9	221.2	204.4
110°	1449.2	1281.7	1082.0	876.4	688.2	520.8	393.8	312.9	262.1	246.5	230.9

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1336.0	1180.1	1009.2	840.6	677.8	527.7	411.1	336.0	287.5	271.9	256.3
115°	1242.5	1107.4	965.3	821.0	675.5	536.9	429.5	360.3	314.1	298.5	282.9
117.5°	1169.7	1060.0	939.9	810.6	674.3	546.2	448.0	383.4	339.5	323.4	307.2
120°	1123.5	1031.1	923.8	802.5	674.3	556.6	467.7	407.6	363.7	347.5	331.4
122.5°	1094.7	1012.7	909.9	793.3	673.2	567.0	486.1	430.7	386.8	371.2	355.6
125°	1072.7	993.0	893.7	782.9	672.0	577.4	504.6	451.5	409.9	393.8	377.6
127.5°	1050.8	971.1	875.3	769.0	669.7	585.4	520.8	471.1	430.7	414.6	398.4
130°	1021.9	943.4	852.2	756.3	668.6	594.7	535.8	490.7	451.5	434.8	418.0
132.5°	988.4	912.2	827.9	744.8	667.4	602.8	550.8	506.9	467.7	452.1	436.5
135°	951.5	881.0	806.0	733.2	666.3	610.8	563.5	521.9	483.8	468.8	453.8
137.5°	912.2	851.0	785.2	722.8	666.3	615.5	572.7	533.5	497.7	483.2	468.8
140°	874.1	822.1	767.9	714.8	665.1	621.2	582.0	545.0	510.4	496.6	482.7
142.5°	840.6	797.9	751.7	707.8	665.1	625.8	588.9	555.4	521.9	508.6	495.4
145°	810.6	776.0	736.7	699.8	662.8	627.0	593.5	562.3	532.3	519.6	506.9
147.5°	785.2	756.3	724.0	692.8	659.3	628.2	598.1	570.4	541.6	530.0	518.5
150°	762.1	739.0	712.5	684.7	655.9	628.2	601.6	576.2	550.8	539.8	528.9
152.5°	742.5	721.7	699.8	675.5	650.1	625.8	603.9	580.8	558.9	549.0	539.2
155°	722.8	705.5	687.0	666.3	644.3	623.5	605.1	585.4	565.8	557.2	548.5
157.5°	704.4	689.4	673.2	657.0	638.6	621.2	605.1	588.9	571.6	564.7	557.7
160°	685.9	673.2	660.5	646.6	631.6	617.8	605.1	591.2	577.4	571.0	564.6
162.5°	667.4	658.2	647.8	637.4	624.7	614.3	605.1	593.5	580.8	576.2	571.6
165°	651.3	643.2	636.2	627.0	617.8	609.7	602.8	593.5	583.1	579.7	576.2
167.5°	637.4	630.5	624.7	617.8	610.8	605.1	600.4	593.5	585.4	582.6	579.7
170°	622.4	617.8	614.3	608.5	603.9	600.4	598.1	592.4	586.6	584.8	583.1
172.5°	609.7	607.4	605.1	600.4	597.0	595.8	595.8	591.2	587.7	586.6	585.4
175°	600.4	598.1	597.0	594.7	592.4	592.4	593.5	590.1	587.7	587.7	587.7
177.5°	592.4	592.4	591.2	590.1	588.9	588.9	591.2	588.9	587.7	587.7	587.7
180°	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7	587.7

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1695.9	1695.9	1695.9	1695.9
2.5°	1657.6	1665.8	1679.5	1698.6
5°	1619.4	1642.6	1664.5	1693.2
7.5°	1585.2	1612.5	1642.6	1683.6
10°	1545.6	1579.7	1618.0	1668.6
12.5°	1499.1	1546.9	1590.7	1645.3
15°	1464.9	1500.5	1556.5	1620.7
17.5°	1417.1	1464.9	1521.0	1593.4
20°	1372.0	1422.6	1485.4	1560.6
22.5°	1324.2	1381.6	1444.4	1525.1
25°	1275.0	1336.5	1399.3	1485.4
27.5°	1229.9	1285.9	1357.0	1444.4
30°	1175.2	1239.5	1307.8	1399.3
32.5°	1121.9	1188.9	1258.6	1350.1
35°	1064.5	1131.5	1208.0	1295.5
37.5°	1008.5	1082.3	1152.0	1236.7
40°	947.0	1023.5	1096.0	1182.1
42.5°	886.9	966.1	1038.6	1112.4
45°	830.9	908.8	974.3	1044.0
47.5°	777.6	847.3	914.2	977.1
50°	725.6	784.4	845.9	897.8
52.5°	671.0	727.0	776.2	822.7
55°	621.8	665.5	709.2	751.6
57.5°	563.0	606.7	645.0	677.8
60°	513.8	541.2	578.0	612.2
62.5°	457.8	489.2	517.9	539.8
65°	403.1	430.5	452.3	471.5
67.5°	356.7	373.1	389.5	410.0
70°	300.6	314.3	333.4	348.5
72.5°	252.8	263.7	273.3	291.1
75°	205.0	214.5	220.0	236.4
77.5°	158.5	168.1	172.2	181.8
80°	121.6	123.0	128.5	136.7
82.5°	83.4	86.1	87.5	94.3
85°	47.8	54.7	53.3	56.0
87.5°	20.5	21.9	24.6	27.3
90°	8.1	6.9	3.5	1.2
92.5°	53.1	35.8	23.1	16.2
95°	68.1	53.1	41.6	38.1
97.5°	87.8	73.9	63.5	63.5
100°	109.7	95.8	87.8	87.8
102.5°	132.8	120.1	113.2	110.9
105°	158.2	144.3	138.6	135.1
107.5°	184.8	169.7	164.0	161.7
110°	210.2	196.3	190.5	188.2

TEST NUMBER: P1025979

CATALOG NUMBER: S124RDIP-B1020D1205UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	235.6	222.9	215.9	213.6
115°	261.0	249.4	241.3	237.9
117.5°	286.4	273.7	266.7	263.3
120°	311.8	299.1	291.0	288.7
122.5°	333.7	322.2	314.1	311.8
125°	355.6	342.9	336.0	331.4
127.5°	375.3	361.4	353.3	349.9
130°	396.1	378.7	369.5	364.9
132.5°	412.2	396.1	383.4	379.9
135°	429.5	409.9	398.4	393.8
137.5°	443.4	424.9	412.2	407.6
140°	458.4	438.8	426.1	422.6
142.5°	472.3	453.8	442.3	438.8
145°	485.0	468.8	457.3	453.8
147.5°	500.0	482.7	472.3	471.1
150°	511.5	497.7	488.4	487.3
152.5°	524.2	511.5	502.3	502.3
155°	535.8	524.2	517.3	516.2
157.5°	546.2	536.9	530.0	530.0
160°	555.4	547.3	542.7	542.7
162.5°	563.5	556.6	553.1	554.3
165°	570.4	564.6	562.3	562.3
167.5°	576.2	571.6	570.4	571.6
170°	580.8	577.4	576.2	577.4
172.5°	584.3	582.0	582.0	583.1
175°	586.6	585.4	585.4	586.6
177.5°	587.7	586.6	587.7	588.9
180°	587.7	587.7	587.7	587.7

(END OF REPORT)