

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026057

Luminaire Tested: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026057
REPORT IS A COMBINATION OF REPORTS P998997 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7144.0 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	66	66	66	60
1	101	97	93	89	94	90	87	84	79	77	74	69	67	65	59	58	57	57	57	57	52
2	92	85	79	74	86	80	75	70	70	66	63	61	58	55	53	50	49	49	49	49	44
3	84	75	68	62	79	71	64	59	62	57	53	54	51	47	47	44	42	42	42	42	38
4	77	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	37	37	37	37	33
5	71	60	52	46	67	56	49	44	50	44	40	44	39	36	38	35	32	32	32	32	29
6	66	54	46	40	62	51	44	38	45	39	35	40	35	32	35	31	28	28	28	28	26
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25	25	25	25	23
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	23	23	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	24	21	21	21	21	19
10	50	37	30	25	46	36	29	25	32	26	23	29	24	21	25	22	19	19	19	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13907	13907	13907	13907
5°	13906	15714	13929	12010
10°	13833	18114	13821	10445
15°	13667	20387	13667	8745
20°	13495	22104	13425	7701
25°	13286	22198	13224	6955
30°	13062	18876	12960	6442
35°	12745	14242	12584	6060
40°	12394	10322	12150	5762
45°	11812	7845	11519	5497
50°	11122	6340	10817	5110
55°	10375	5250	10036	4595
60°	9623	4439	9195	3821
65°	8682	3616	8406	3037
70°	7817	2933	7449	2467
75°	6850	2113	6374	1808
80°	5651	1401	5145	1330
85°	4097	721	3398	721

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 17409 cd/sqm

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.1	2.3
10°-20°	498.7	7.0
20°-30°	781.1	10.9
30°-40°	867.4	12.1
40°-50°	768.7	10.8
50°-60°	599.0	8.4
60°-70°	391.8	5.5
70°-80°	192.3	2.7
80°-90°	48.3	0.7
90°-100°	281.8	3.9
100°-110°	588.2	8.2
110°-120°	522.9	7.3
120°-130°	440.2	6.2
130°-140°	367.2	5.1
140°-150°	280.4	3.9
150°-160°	197.1	2.8
160°-170°	115.9	1.6
170°-180°	37.7	0.5
0°-30°	1445.0	20.2
0°-40°	2312.4	32.4
0°-60°	3680.1	51.5
0°-90°	4312.5	60.4
90°-120°	1392.9	19.5
90°-150°	2480.7	34.7
90°-180°	2831.0	39.6
0°-180°	7144.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1705	1705	1705	1705	1705	
5°	1703	1971	1705	1506	1703	162
15°	1630	2611	1630	1120	1630	460
25°	1494	2816	1487	882	1494	688
35°	1303	1734	1286	738	1303	814
45°	1050	886	1024	621	1050	810
55°	756	529	731	463	756	676
65°	474	309	459	260	474	473
75°	238	143	221	122	238	252
85°	56	34	47	34	56	64
90°	1	16	1	16	1	5
95°	25	186	25	186	25	28
105°	89	1075	89	1075	89	95
115°	157	1032	157	1032	157	156
125°	219	823	219	823	219	195
135°	260	736	260	736	260	201
145°	300	601	300	601	300	188
155°	341	503	341	503	341	157
165°	372	439	372	439	372	105
175°	388	396	388	396	388	37
180°	389	389	389	389	389	

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1708.1	1723.2	1731.5	1738.4	1752.1	1757.6	1768.6	1771.3	1782.3	1781.0	1776.8
5°	1702.6	1728.7	1748.0	1768.6	1793.3	1807.1	1822.2	1844.2	1855.2	1870.3	1879.9
7.5°	1693.0	1728.7	1760.3	1792.0	1831.8	1853.8	1873.0	1907.4	1936.2	1961.0	1988.5
10°	1677.9	1723.2	1770.0	1812.6	1867.5	1893.6	1922.5	1973.3	2013.2	2047.6	2091.5
12.5°	1654.5	1717.7	1770.0	1827.7	1897.8	1933.5	1972.0	2032.4	2079.2	2135.5	2190.5
15°	1629.8	1699.9	1768.6	1844.2	1923.9	1965.1	2003.6	2084.7	2156.1	2220.7	2281.2
17.5°	1602.3	1679.3	1754.9	1838.7	1934.9	1985.7	2031.1	2128.6	2207.0	2290.8	2351.3
20°	1569.3	1653.2	1739.7	1833.2	1941.7	1998.1	2048.9	2160.2	2246.8	2337.5	2413.1
22.5°	1533.6	1624.3	1719.1	1820.8	1933.5	1995.3	2054.4	2174.0	2274.3	2358.1	2459.8
25°	1493.8	1589.9	1687.5	1794.7	1921.1	1988.5	2048.9	2167.1	2274.3	2384.2	2483.2
27.5°	1452.5	1551.5	1653.2	1765.8	1895.0	1961.0	2029.7	2143.7	2268.8	2388.4	2488.7
30°	1407.2	1503.4	1610.6	1717.7	1855.2	1921.1	1991.2	2114.9	2250.9	2370.5	2479.1
32.5°	1357.7	1456.6	1558.3	1669.7	1804.3	1875.8	1940.4	2080.5	2219.3	2337.5	2439.2
35°	1302.7	1396.2	1492.4	1606.4	1739.7	1804.3	1881.3	2026.9	2167.1	2292.2	2358.1
37.5°	1243.6	1333.0	1422.3	1535.0	1662.8	1741.1	1816.7	1963.7	2112.1	2196.0	2230.3
40°	1188.7	1267.0	1345.3	1453.9	1583.1	1664.2	1741.1	1893.6	2024.2	2088.8	2062.7
42.5°	1118.6	1199.7	1269.8	1370.1	1500.6	1576.2	1654.5	1812.6	1918.4	1944.5	1879.9
45°	1049.9	1117.2	1184.6	1282.1	1419.5	1484.1	1568.0	1715.0	1802.9	1779.6	1684.8
47.5°	982.6	1037.5	1100.7	1195.6	1319.2	1396.2	1474.5	1602.3	1664.2	1631.2	1499.3
50°	902.8	957.8	1023.8	1106.2	1225.8	1300.0	1361.8	1480.0	1526.7	1445.7	1286.2
52.5°	827.3	875.4	931.7	1008.7	1122.7	1190.1	1257.4	1359.1	1374.2	1280.8	1113.1
55°	755.8	794.3	853.4	915.2	1019.7	1091.1	1137.8	1224.4	1220.3	1103.5	959.2
57.5°	681.6	717.3	757.2	821.8	920.7	974.3	1025.2	1100.7	1060.9	961.9	819.0
60°	615.6	636.3	676.1	737.9	821.8	868.5	908.3	949.6	915.2	808.0	698.1
62.5°	542.8	566.2	595.0	644.5	718.7	762.7	791.5	809.4	773.7	691.2	590.9
65°	474.1	494.7	524.9	568.9	625.3	658.2	673.4	685.7	666.5	573.0	493.3
67.5°	412.3	426.0	453.5	482.3	542.8	551.1	571.7	577.2	538.7	467.2	404.0
70°	350.4	364.2	376.5	410.9	438.4	453.5	457.6	457.6	419.1	372.4	320.2
72.5°	292.7	300.9	313.3	336.7	351.8	362.8	368.3	361.4	325.7	287.2	248.7
75°	237.7	241.9	252.9	268.0	280.3	276.2	274.8	266.6	240.5	213.0	191.0
77.5°	182.8	185.5	197.9	202.0	202.0	206.1	200.6	192.4	170.4	149.8	140.2
80°	137.4	141.5	142.9	145.7	142.9	142.9	138.8	125.1	114.1	104.4	97.6
82.5°	94.8	97.6	98.9	94.8	97.6	93.4	86.6	77.0	70.1	68.7	66.0
85°	56.3	57.7	56.3	56.3	52.2	50.8	45.3	44.0	41.2	41.2	39.9
87.5°	27.5	26.1	23.4	20.6	20.6	19.2	20.6	17.9	20.6	19.2	17.9
90°	0.8	2.3	4.6	5.3	6.1	6.1	6.1	10.7	10.7	12.2	13.7
92.5°	10.7	15.3	23.7	35.1	48.9	58.8	68.7	116.1	190.2	262.0	299.4
95°	25.2	27.5	35.1	45.1	63.4	79.4	95.5	161.9	287.2	469.7	622.5
97.5°	42.0	42.0	48.9	58.0	74.1	87.8	101.6	154.3	262.0	449.9	666.0
100°	58.0	58.0	63.4	72.6	87.1	99.3	111.5	156.6	242.9	398.7	614.1
102.5°	73.3	74.9	79.4	87.8	101.6	113.0	124.5	164.2	237.5	364.3	549.2
105°	89.4	91.7	95.5	104.6	118.4	129.4	140.5	177.2	240.6	347.5	501.0
107.5°	106.9	108.5	112.3	122.2	135.2	146.2	157.3	190.9	249.8	342.9	469.7
110°	124.5	126.0	129.8	139.0	152.8	163.1	173.4	207.0	260.4	344.5	455.2

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	141.3	142.8	147.4	155.8	169.6	179.9	190.2	222.3	271.9	349.0	448.3
115°	157.3	159.6	165.0	172.6	187.1	197.4	207.7	238.3	284.1	355.2	446.8
117.5°	174.1	176.4	181.0	189.4	203.2	213.9	224.6	253.6	296.3	361.3	446.0
120°	190.9	192.5	197.8	206.2	219.2	229.9	240.6	269.6	309.3	368.1	446.0
122.5°	206.2	207.7	213.1	220.7	235.2	245.6	255.9	284.9	321.6	375.0	445.3
125°	219.2	222.3	226.8	235.2	249.8	260.5	271.1	298.6	333.8	381.9	444.5
127.5°	231.4	233.7	239.1	248.2	263.5	274.2	284.9	311.6	344.5	387.2	443.0
130°	241.4	244.4	250.5	262.0	276.5	287.6	298.6	324.6	354.4	393.3	442.2
132.5°	251.3	253.6	262.0	272.7	288.7	299.0	309.3	335.3	364.3	398.7	441.5
135°	260.4	263.5	271.1	284.1	300.2	310.1	320.0	345.2	372.7	404.0	440.7
137.5°	269.6	272.7	281.1	293.3	310.1	319.6	329.2	352.9	378.8	407.1	440.7
140°	279.5	281.8	290.2	303.2	319.3	328.5	337.6	360.5	384.9	410.9	439.9
142.5°	290.2	292.5	300.2	312.4	327.7	336.4	345.2	367.4	389.5	414.0	439.9
145°	300.2	302.5	310.1	320.8	335.3	343.7	352.1	372.0	392.6	414.7	438.4
147.5°	311.6	312.4	319.3	330.7	342.9	350.5	358.2	377.3	395.6	415.5	436.1
150°	322.3	323.1	329.2	338.4	349.8	357.0	364.3	381.1	397.9	415.5	433.8
152.5°	332.2	332.2	338.4	346.8	356.7	363.2	369.7	384.2	399.5	414.0	430.0
155°	341.4	342.2	346.8	354.4	362.8	368.6	374.3	387.2	400.2	412.4	426.2
157.5°	350.6	350.6	355.2	361.3	368.9	373.5	378.1	389.5	400.2	410.9	422.4
160°	359.0	359.0	362.0	367.4	373.5	377.7	381.9	391.1	400.2	408.6	417.8
162.5°	366.6	365.9	368.1	372.7	378.1	381.2	384.2	392.6	400.2	406.3	413.2
165°	372.0	372.0	373.5	377.3	381.1	383.4	385.7	392.6	398.7	403.3	408.6
167.5°	378.1	377.3	378.1	381.1	383.4	385.3	387.2	392.6	397.2	400.2	404.0
170°	381.9	381.1	381.9	384.2	385.7	386.8	388.0	391.8	395.6	397.2	399.5
172.5°	385.7	384.9	384.9	386.5	387.2	388.0	388.8	391.1	394.1	394.1	394.9
175°	388.0	387.2	387.2	388.0	388.8	388.8	388.8	390.3	392.6	391.8	391.8
177.5°	389.5	388.8	388.0	388.8	388.8	388.8	388.8	389.5	391.1	389.5	389.5
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1787.8	1802.9	1804.3	1818.1	1813.9	1807.1	1819.4	1811.2	1827.7	1822.2	1829.1
5°	1892.3	1912.9	1930.7	1941.7	1961.0	1956.9	1977.5	1970.6	1985.7	1970.6	1989.8
7.5°	2014.6	2048.9	2066.8	2095.7	2103.9	2105.3	2130.0	2135.5	2145.1	2135.5	2146.5
10°	2134.1	2175.4	2216.6	2239.9	2255.1	2275.7	2297.7	2307.3	2314.1	2304.5	2311.4
12.5°	2242.7	2307.3	2352.6	2399.3	2410.3	2428.2	2451.6	2448.8	2476.3	2470.8	2483.2
15°	2343.0	2414.5	2469.4	2506.5	2536.8	2551.9	2595.9	2598.6	2597.2	2611.0	2602.7
17.5°	2432.3	2492.8	2571.1	2619.2	2656.3	2656.3	2681.1	2731.9	2727.8	2726.4	2734.7
20°	2505.2	2573.9	2646.7	2727.8	2758.0	2763.5	2797.9	2824.0	2828.1	2828.1	2828.1
22.5°	2560.1	2641.2	2719.5	2777.3	2800.6	2819.9	2850.1	2866.6	2872.1	2869.3	2872.1
25°	2587.6	2664.6	2744.3	2796.5	2810.2	2821.2	2824.0	2833.6	2832.2	2815.7	2825.4
27.5°	2593.1	2667.3	2719.5	2733.3	2726.4	2719.5	2675.6	2679.7	2667.3	2642.6	2652.2
30°	2568.4	2608.2	2606.9	2564.3	2551.9	2523.0	2483.2	2424.1	2376.0	2355.4	2362.2
32.5°	2479.1	2479.1	2429.6	2333.4	2290.8	2238.6	2167.1	2113.5	2050.3	2036.6	2062.7
35°	2355.4	2285.3	2194.6	2068.2	2003.6	1965.1	1841.4	1802.9	1749.4	1734.2	1746.6
37.5°	2163.0	2046.2	1914.3	1796.1	1741.1	1672.4	1563.8	1508.9	1470.4	1444.3	1456.6
40°	1947.2	1805.7	1668.3	1522.6	1462.1	1405.8	1324.7	1275.3	1213.4	1216.2	1220.3
42.5°	1741.1	1574.8	1420.9	1286.2	1228.5	1181.8	1125.5	1065.0	1043.0	1036.1	1029.3
45°	1522.6	1345.3	1201.0	1100.7	1048.5	1004.5	952.3	918.0	891.9	886.4	893.2
47.5°	1316.5	1166.7	1029.3	935.8	893.2	871.2	830.0	798.4	781.9	768.2	776.4
50°	1129.6	989.4	879.5	801.2	770.9	755.8	717.3	700.8	684.4	680.2	678.9
52.5°	975.7	856.1	761.3	698.1	674.7	666.5	637.6	614.3	600.5	604.6	607.4
55°	835.5	733.8	659.6	608.8	589.5	579.9	559.3	542.8	533.2	529.1	531.8
57.5°	711.8	623.9	570.3	529.1	514.0	509.8	487.8	482.3	475.5	471.3	471.3
60°	599.2	537.3	487.8	464.5	448.0	443.9	427.4	420.5	419.1	415.0	412.3
62.5°	504.3	453.5	419.1	394.4	387.5	386.1	375.2	366.9	362.8	360.0	360.0
65°	421.9	384.8	355.9	338.1	332.6	329.8	317.4	314.7	311.9	309.2	307.8
67.5°	351.8	318.8	298.2	285.8	279.0	280.3	273.5	268.0	268.0	266.6	265.2
70°	284.5	263.8	246.0	239.1	236.4	233.6	230.9	226.7	225.4	225.4	225.4
72.5°	224.0	210.3	200.6	196.5	193.8	191.0	188.3	188.3	188.3	186.9	186.9
75°	171.8	166.3	159.4	155.3	155.3	158.0	153.9	149.8	145.7	142.9	144.3
77.5°	129.2	126.4	122.3	115.4	116.8	114.1	114.1	111.3	112.7	112.7	109.9
80°	94.8	90.7	89.3	85.2	86.6	85.2	83.8	83.8	81.1	81.1	81.1
82.5°	66.0	61.8	61.8	60.5	59.1	59.1	57.7	57.7	59.1	56.3	56.3
85°	39.9	38.5	38.5	35.7	35.7	35.7	35.7	37.1	35.7	34.4	34.4
87.5°	17.9	19.2	17.9	16.5	16.5	16.5	15.1	15.1	13.7	15.1	15.1
90°	13.0	13.7	14.5	15.3	15.3	15.3	16.0	16.8	16.0	16.0	16.0
92.5°	249.0	184.1	137.5	108.5	99.0	89.4	77.9	72.6	69.5	69.5	69.5
95°	640.0	566.0	447.6	345.2	308.2	271.1	233.7	210.0	196.3	186.4	196.3
97.5°	802.7	815.0	756.1	672.1	629.4	586.6	534.6	488.8	465.9	447.6	465.9
100°	809.6	921.1	936.4	899.0	870.8	842.5	776.0	729.4	706.5	700.4	706.5
102.5°	752.3	915.8	1006.7	1029.6	1022.0	1014.3	979.9	949.4	924.9	920.4	924.9
105°	680.5	855.4	987.6	1063.2	1078.8	1094.5	1096.0	1089.9	1079.2	1074.6	1079.2
107.5°	621.7	781.3	924.2	1029.6	1061.6	1093.7	1127.3	1141.1	1147.2	1148.0	1147.2
110°	579.7	715.7	847.8	958.5	1000.6	1042.6	1096.8	1128.9	1142.6	1149.5	1142.6

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	556.0	667.5	780.6	883.7	925.7	967.7	1031.1	1071.6	1092.2	1104.4	1092.2
115°	543.0	638.5	732.5	821.8	858.5	895.2	955.5	1001.3	1025.8	1031.9	1025.8
117.5°	536.2	621.7	701.2	773.7	805.8	837.9	891.3	931.0	957.0	960.8	957.0
120°	530.8	611.0	682.1	743.2	770.3	797.4	840.9	874.5	894.4	902.8	894.4
122.5°	524.7	601.9	669.8	724.1	747.0	769.9	805.0	832.5	848.6	857.0	848.6
125°	517.8	591.2	656.9	709.6	730.6	751.6	782.1	804.3	818.8	823.4	818.8
127.5°	508.7	578.9	642.3	695.0	714.9	734.8	765.3	785.2	797.4	802.0	797.4
130°	500.3	563.7	624.0	675.9	696.2	716.4	747.7	766.8	779.1	783.6	779.1
132.5°	492.6	547.6	603.4	653.8	674.0	694.3	724.8	747.0	758.4	763.0	758.4
135°	485.0	533.1	582.8	629.4	648.4	667.5	698.1	719.5	731.7	736.3	731.7
137.5°	478.1	519.4	562.9	603.4	621.0	638.5	667.5	689.7	699.6	705.0	699.6
140°	472.8	507.9	543.8	578.2	594.2	610.3	637.0	653.8	664.5	670.6	664.5
142.5°	468.2	497.2	527.8	556.0	569.4	582.8	605.7	621.0	630.1	633.9	630.1
145°	462.9	487.3	513.3	536.2	546.9	557.6	576.7	589.6	597.3	601.1	597.3
147.5°	458.3	478.9	500.3	519.4	528.2	536.9	551.4	562.9	569.0	570.5	569.0
150°	452.9	471.3	488.8	504.1	511.0	517.8	530.1	540.0	544.6	545.3	544.6
152.5°	446.8	462.9	477.4	491.1	496.4	501.8	511.7	519.4	521.7	522.4	521.7
155°	440.7	454.4	466.7	478.1	482.7	487.3	494.9	501.0	503.3	503.3	503.3
157.5°	434.6	445.3	456.0	465.9	469.7	473.5	479.7	484.2	485.8	485.8	485.8
160°	427.7	436.9	445.3	453.7	456.8	459.8	464.4	469.0	469.7	469.7	469.7
162.5°	421.6	428.5	435.4	441.5	444.2	446.8	449.9	454.4	455.2	454.4	455.2
165°	414.7	420.8	425.4	430.8	432.7	434.6	437.6	440.7	439.9	439.2	439.9
167.5°	408.6	413.2	417.0	421.6	422.8	423.9	425.4	427.7	427.7	427.0	427.7
170°	402.5	406.3	408.6	411.7	412.8	414.0	415.5	416.3	415.5	415.5	415.5
172.5°	397.2	400.2	401.7	403.3	404.0	404.8	405.6	406.3	405.6	404.0	405.6
175°	393.3	394.9	395.6	397.2	397.2	397.2	397.2	398.7	397.2	395.6	397.2
177.5°	390.3	391.1	391.8	391.8	392.2	392.6	391.8	392.6	391.1	389.5	391.1
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1833.2	1823.6	1822.2	1822.2	1807.1	1815.3	1798.8	1781.0	1772.7	1772.7	1757.6
5°	1985.7	1976.1	1966.5	1951.4	1951.4	1943.1	1917.0	1890.9	1871.7	1855.2	1837.3
7.5°	2142.4	2132.8	2105.3	2090.2	2098.4	2081.9	2047.6	2003.6	1970.6	1944.5	1907.4
10°	2312.8	2286.7	2272.9	2264.7	2235.8	2218.0	2178.1	2113.5	2072.3	2037.9	1989.8
12.5°	2451.6	2459.8	2407.6	2411.7	2382.9	2358.1	2296.3	2234.4	2172.6	2124.5	2053.1
15°	2601.4	2576.6	2545.0	2520.3	2510.7	2480.4	2428.2	2345.8	2278.4	2202.8	2121.8
17.5°	2719.5	2700.3	2670.1	2646.7	2626.1	2553.3	2509.3	2436.5	2344.4	2270.2	2171.2
20°	2819.9	2802.0	2759.4	2744.3	2707.2	2655.0	2591.7	2479.1	2396.6	2315.5	2219.3
22.5°	2862.5	2844.6	2807.5	2788.2	2764.9	2714.0	2653.6	2546.4	2444.7	2343.0	2241.3
25°	2826.7	2826.7	2808.9	2802.0	2781.4	2736.0	2674.2	2583.5	2474.9	2365.0	2244.1
27.5°	2653.6	2687.9	2700.3	2707.2	2707.2	2708.5	2665.9	2578.0	2472.2	2365.0	2238.6
30°	2403.5	2461.2	2512.0	2527.2	2553.3	2582.1	2600.0	2557.4	2462.6	2349.9	2223.5
32.5°	2088.8	2163.0	2257.8	2281.2	2316.9	2403.5	2451.6	2469.4	2417.2	2318.3	2183.6
35°	1775.5	1868.9	1926.6	1998.1	2031.1	2158.9	2266.1	2330.6	2318.3	2259.2	2136.9
37.5°	1502.0	1555.6	1625.7	1701.3	1767.2	1889.5	2022.8	2147.9	2198.7	2169.9	2077.8
40°	1239.5	1302.7	1386.6	1448.4	1493.8	1616.1	1781.0	1917.0	2028.3	2046.2	1989.8
42.5°	1054.0	1117.2	1168.1	1235.4	1271.1	1389.3	1535.0	1705.4	1837.3	1907.4	1882.7
45°	911.1	949.6	990.8	1029.3	1073.2	1177.7	1312.4	1499.3	1647.7	1746.6	1756.2
47.5°	786.0	820.4	856.1	891.9	916.6	997.7	1121.3	1273.9	1436.0	1572.1	1625.7
50°	698.1	714.6	740.7	761.3	790.2	860.2	959.2	1091.1	1262.9	1409.9	1480.0
52.5°	611.5	632.1	652.7	670.6	689.8	739.3	830.0	944.1	1092.5	1243.6	1330.2
55°	538.7	555.2	574.4	586.8	597.8	641.8	710.5	798.4	926.2	1069.1	1176.3
57.5°	479.6	486.5	503.0	509.8	522.2	557.9	607.4	685.7	788.8	927.6	1015.5
60°	415.0	428.7	441.1	446.6	456.2	481.0	515.3	588.2	677.5	779.2	879.5
62.5°	362.8	368.3	377.9	384.8	391.6	417.8	446.6	501.6	568.9	654.1	746.2
65°	314.7	317.4	322.9	332.6	336.7	355.9	372.4	412.3	475.5	540.1	632.1
67.5°	265.2	268.0	274.8	280.3	284.5	296.8	314.7	343.5	377.9	449.4	500.2
70°	226.7	226.7	230.9	233.6	237.7	243.2	252.9	274.8	306.4	351.8	398.5
72.5°	189.6	189.6	189.6	193.8	193.8	197.9	203.4	218.5	240.5	276.2	306.4
75°	147.0	148.4	151.2	151.2	152.5	158.0	162.2	166.3	177.3	200.6	228.1
77.5°	111.3	114.1	115.4	112.7	115.4	115.4	120.9	126.4	131.9	138.8	159.4
80°	82.5	83.8	81.1	82.5	82.5	85.2	87.9	86.6	89.3	97.6	103.1
82.5°	55.0	56.3	56.3	56.3	56.3	60.5	60.5	59.1	60.5	61.8	63.2
85°	34.4	33.0	33.0	34.4	33.0	33.0	34.4	35.7	34.4	35.7	37.1
87.5°	15.1	15.1	15.1	15.1	13.7	13.7	15.1	13.7	15.1	13.7	12.4
90°	16.8	16.0	15.3	15.3	15.3	14.5	13.7	13.0	13.7	12.2	10.7
92.5°	72.6	77.9	89.4	99.0	108.5	137.5	184.1	249.0	299.4	262.0	190.2
95°	210.0	233.7	271.1	308.2	345.2	447.6	566.0	640.0	622.5	469.7	287.2
97.5°	488.8	534.6	586.6	629.4	672.1	756.1	815.0	802.7	666.0	449.9	262.0
100°	729.4	776.0	842.5	870.8	899.0	936.4	921.1	809.6	614.1	398.7	242.9
102.5°	949.4	979.9	1014.3	1022.0	1029.6	1006.7	915.8	752.3	549.2	364.3	237.5
105°	1089.9	1096.0	1094.5	1078.8	1063.2	987.6	855.4	680.5	501.0	347.5	240.6
107.5°	1141.1	1127.3	1093.7	1061.6	1029.6	924.2	781.3	621.7	469.7	342.9	249.8
110°	1128.9	1096.8	1042.6	1000.6	958.5	847.8	715.7	579.7	455.2	344.5	260.4

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1071.6	1031.1	967.7	925.7	883.7	780.6	667.5	556.0	448.3	349.0	271.9
115°	1001.3	955.5	895.2	858.5	821.8	732.5	638.5	543.0	446.8	355.2	284.1
117.5°	931.0	891.3	837.9	805.8	773.7	701.2	621.7	536.2	446.0	361.3	296.3
120°	874.5	840.9	797.4	770.3	743.2	682.1	611.0	530.8	446.0	368.1	309.3
122.5°	832.5	805.0	769.9	747.0	724.1	669.8	601.9	524.7	445.3	375.0	321.6
125°	804.3	782.1	751.6	730.6	709.6	656.9	591.2	517.8	444.5	381.9	333.8
127.5°	785.2	765.3	734.8	714.9	695.0	642.3	578.9	508.7	443.0	387.2	344.5
130°	766.8	747.7	716.4	696.2	675.9	624.0	563.7	500.3	442.2	393.3	354.4
132.5°	747.0	724.8	694.3	674.0	653.8	603.4	547.6	492.6	441.5	398.7	364.3
135°	719.5	698.1	667.5	648.4	629.4	582.8	533.1	485.0	440.7	404.0	372.7
137.5°	689.7	667.5	638.5	621.0	603.4	562.9	519.4	478.1	440.7	407.1	378.8
140°	653.8	637.0	610.3	594.2	578.2	543.8	507.9	472.8	439.9	410.9	384.9
142.5°	621.0	605.7	582.8	569.4	556.0	527.8	497.2	468.2	439.9	414.0	389.5
145°	589.6	576.7	557.6	546.9	536.2	513.3	487.3	462.9	438.4	414.7	392.6
147.5°	562.9	551.4	536.9	528.2	519.4	500.3	478.9	458.3	436.1	415.5	395.6
150°	540.0	530.1	517.8	511.0	504.1	488.8	471.3	452.9	433.8	415.5	397.9
152.5°	519.4	511.7	501.8	496.4	491.1	477.4	462.9	446.8	430.0	414.0	399.5
155°	501.0	494.9	487.3	482.7	478.1	466.7	454.4	440.7	426.2	412.4	400.2
157.5°	484.2	479.7	473.5	469.7	465.9	456.0	445.3	434.6	422.4	410.9	400.2
160°	469.0	464.4	459.8	456.8	453.7	445.3	436.9	427.7	417.8	408.6	400.2
162.5°	454.4	449.9	446.8	444.2	441.5	435.4	428.5	421.6	413.2	406.3	400.2
165°	440.7	437.6	434.6	432.7	430.8	425.4	420.8	414.7	408.6	403.3	398.7
167.5°	427.7	425.4	423.9	422.8	421.6	417.0	413.2	408.6	404.0	400.2	397.2
170°	416.3	415.5	414.0	412.8	411.7	408.6	406.3	402.5	399.5	397.2	395.6
172.5°	406.3	405.6	404.8	404.0	403.3	401.7	400.2	397.2	394.9	394.1	394.1
175°	398.7	397.2	397.2	397.2	397.2	395.6	394.9	393.3	391.8	391.8	392.6
177.5°	392.6	391.8	392.6	392.2	391.8	391.8	391.1	390.3	389.5	389.5	391.1
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1749.4	1742.5	1738.4	1737.0	1724.6	1717.7	1713.6	1710.9	1706.8	1695.8	1686.1
5°	1815.3	1796.1	1786.5	1775.5	1756.2	1734.2	1716.4	1705.4	1691.6	1669.7	1649.0
7.5°	1877.2	1848.3	1829.1	1813.9	1781.0	1745.2	1716.4	1693.0	1666.9	1636.7	1607.8
10°	1941.7	1895.0	1870.3	1846.9	1798.8	1752.1	1710.9	1676.5	1639.4	1599.6	1568.0
12.5°	1992.6	1930.7	1903.3	1870.3	1811.2	1756.2	1704.0	1657.3	1609.2	1566.6	1521.2
15°	2051.7	1974.7	1943.1	1900.5	1819.4	1748.0	1680.6	1629.8	1580.3	1517.1	1469.0
17.5°	2086.0	1996.7	1951.4	1914.3	1826.3	1739.7	1661.4	1598.2	1540.5	1477.3	1426.4
20°	2120.4	2018.7	1967.9	1915.6	1811.2	1719.1	1636.7	1561.1	1500.6	1431.9	1379.7
22.5°	2131.4	2013.2	1959.6	1911.5	1801.6	1698.5	1603.7	1526.7	1456.6	1387.9	1328.8
25°	2131.4	2011.8	1948.6	1886.8	1771.3	1665.5	1570.7	1486.9	1408.6	1339.8	1280.8
27.5°	2109.4	1984.3	1918.4	1862.0	1742.5	1628.4	1530.9	1438.8	1363.2	1294.5	1227.2
30°	2081.9	1944.5	1878.5	1811.2	1695.8	1587.2	1481.4	1396.2	1316.5	1238.2	1177.7
32.5°	2047.6	1901.9	1829.1	1760.3	1638.0	1525.4	1427.8	1344.0	1268.4	1187.3	1120.0
35°	1998.1	1838.7	1757.6	1697.1	1579.0	1462.1	1368.7	1286.2	1213.4	1129.6	1056.8
37.5°	1934.9	1781.0	1698.5	1624.3	1502.0	1394.8	1306.9	1227.2	1155.7	1078.7	997.7
40°	1860.7	1699.9	1628.4	1550.1	1420.9	1319.2	1236.8	1165.3	1093.9	1021.0	942.7
42.5°	1776.8	1617.4	1537.7	1462.1	1338.5	1238.2	1161.2	1096.6	1030.6	963.3	879.5
45°	1676.5	1526.7	1449.8	1378.3	1258.8	1155.7	1085.6	1023.8	967.4	898.7	824.5
47.5°	1563.8	1433.3	1355.0	1278.0	1161.2	1071.9	1003.2	950.9	902.8	834.1	766.8
50°	1453.9	1324.7	1261.5	1183.2	1076.0	992.2	922.1	878.1	841.0	773.7	713.2
52.5°	1315.1	1217.5	1157.1	1089.7	986.7	901.5	846.5	808.0	764.1	711.8	658.2
55°	1192.8	1102.1	1054.0	990.8	889.1	813.5	766.8	731.1	696.7	650.0	607.4
57.5°	1054.0	997.7	949.6	894.6	794.3	729.7	688.5	658.2	626.6	588.2	553.8
60°	908.3	882.2	835.5	791.5	706.3	650.0	615.6	588.2	557.9	526.3	497.5
62.5°	779.2	764.1	736.6	702.2	622.5	574.4	540.1	519.4	497.5	468.6	441.1
65°	656.9	650.0	623.9	599.2	544.2	501.6	471.3	459.0	434.2	412.3	387.5
67.5°	548.3	540.1	524.9	514.0	467.2	427.4	412.3	395.8	375.2	358.7	338.1
70°	438.4	437.0	427.4	413.6	388.9	360.0	344.9	333.9	313.3	300.9	285.8
72.5°	340.8	347.7	339.4	333.9	317.4	296.8	283.1	276.2	259.7	250.1	239.1
75°	254.2	259.7	263.8	254.2	250.1	240.5	228.1	221.2	213.0	199.3	195.1
77.5°	173.1	185.5	185.5	188.3	189.6	184.1	174.5	169.0	159.4	156.7	151.2
80°	114.1	125.1	126.4	129.2	133.3	133.3	126.4	125.1	115.4	114.1	109.9
82.5°	66.0	75.6	81.1	85.2	83.8	89.3	83.8	82.5	77.0	77.0	74.2
85°	35.7	37.1	39.9	42.6	45.3	48.1	48.1	46.7	45.3	44.0	41.2
87.5°	13.7	13.7	15.1	13.7	15.1	17.9	19.2	19.2	17.9	16.5	13.7
90°	10.7	6.1	6.1	6.1	5.3	4.6	2.3	0.8	2.3	4.6	5.3
92.5°	116.1	68.7	58.8	48.9	35.1	23.7	15.3	10.7	15.3	23.7	35.1
95°	161.9	95.5	79.4	63.4	45.1	35.1	27.5	25.2	27.5	35.1	45.1
97.5°	154.3	101.6	87.8	74.1	58.0	48.9	42.0	42.0	42.0	48.9	58.0
100°	156.6	111.5	99.3	87.1	72.6	63.4	58.0	58.0	58.0	63.4	72.6
102.5°	164.2	124.5	113.0	101.6	87.8	79.4	74.9	73.3	74.9	79.4	87.8
105°	177.2	140.5	129.4	118.4	104.6	95.5	91.7	89.4	91.7	95.5	104.6
107.5°	190.9	157.3	146.2	135.2	122.2	112.3	108.5	106.9	108.5	112.3	122.2
110°	207.0	173.4	163.1	152.8	139.0	129.8	126.0	124.5	126.0	129.8	139.0

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	222.3	190.2	179.9	169.6	155.8	147.4	142.8	141.3	142.8	147.4	155.8
115°	238.3	207.7	197.4	187.1	172.6	165.0	159.6	157.3	159.6	165.0	172.6
117.5°	253.6	224.6	213.9	203.2	189.4	181.0	176.4	174.1	176.4	181.0	189.4
120°	269.6	240.6	229.9	219.2	206.2	197.8	192.5	190.9	192.5	197.8	206.2
122.5°	284.9	255.9	245.6	235.2	220.7	213.1	207.7	206.2	207.7	213.1	220.7
125°	298.6	271.1	260.5	249.8	235.2	226.8	222.3	219.2	222.3	226.8	235.2
127.5°	311.6	284.9	274.2	263.5	248.2	239.1	233.7	231.4	233.7	239.1	248.2
130°	324.6	298.6	287.6	276.5	262.0	250.5	244.4	241.4	244.4	250.5	262.0
132.5°	335.3	309.3	299.0	288.7	272.7	262.0	253.6	251.3	253.6	262.0	272.7
135°	345.2	320.0	310.1	300.2	284.1	271.1	263.5	260.4	263.5	271.1	284.1
137.5°	352.9	329.2	319.6	310.1	293.3	281.1	272.7	269.6	272.7	281.1	293.3
140°	360.5	337.6	328.5	319.3	303.2	290.2	281.8	279.5	281.8	290.2	303.2
142.5°	367.4	345.2	336.4	327.7	312.4	300.2	292.5	290.2	292.5	300.2	312.4
145°	372.0	352.1	343.7	335.3	320.8	310.1	302.5	300.2	302.5	310.1	320.8
147.5°	377.3	358.2	350.5	342.9	330.7	319.3	312.4	311.6	312.4	319.3	330.7
150°	381.1	364.3	357.0	349.8	338.4	329.2	323.1	322.3	323.1	329.2	338.4
152.5°	384.2	369.7	363.2	356.7	346.8	338.4	332.2	332.2	332.2	338.4	346.8
155°	387.2	374.3	368.6	362.8	354.4	346.8	342.2	341.4	342.2	346.8	354.4
157.5°	389.5	378.1	373.5	368.9	361.3	355.2	350.6	350.6	350.6	355.2	361.3
160°	391.1	381.9	377.7	373.5	367.4	362.0	359.0	359.0	359.0	362.0	367.4
162.5°	392.6	384.2	381.2	378.1	372.7	368.1	365.9	366.6	365.9	368.1	372.7
165°	392.6	385.7	383.4	381.1	377.3	373.5	372.0	372.0	372.0	373.5	377.3
167.5°	392.6	387.2	385.3	383.4	381.1	378.1	377.3	378.1	377.3	378.1	381.1
170°	391.8	388.0	386.8	385.7	384.2	381.9	381.1	381.9	381.1	381.9	384.2
172.5°	391.1	388.8	388.0	387.2	386.5	384.9	384.9	385.7	384.9	384.9	386.5
175°	390.3	388.8	388.8	388.8	388.0	387.2	387.2	388.0	387.2	387.2	388.0
177.5°	389.5	388.8	388.8	388.8	388.8	388.0	388.8	389.5	388.8	388.0	388.8
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1677.9	1675.1	1672.4	1661.4	1651.8	1635.3	1621.6	1616.1	1614.7	1616.1	1611.9
5°	1629.8	1628.4	1618.8	1599.6	1581.7	1562.5	1548.7	1535.0	1526.7	1526.7	1517.1
7.5°	1584.5	1574.8	1566.6	1541.9	1521.2	1495.1	1474.5	1462.1	1455.3	1440.2	1440.2
10°	1536.4	1522.6	1511.6	1488.3	1458.0	1431.9	1405.8	1390.7	1378.3	1367.3	1363.2
12.5°	1488.3	1477.3	1456.6	1431.9	1401.7	1368.7	1341.2	1330.2	1301.4	1278.0	1279.4
15°	1442.9	1418.2	1408.6	1372.8	1337.1	1305.5	1265.6	1234.0	1210.7	1195.6	1176.3
17.5°	1392.1	1367.3	1349.5	1319.2	1272.5	1223.0	1184.6	1142.0	1118.6	1092.5	1080.1
20°	1335.7	1315.1	1301.4	1253.3	1196.9	1137.8	1095.2	1069.1	1043.0	1023.8	1012.8
22.5°	1287.6	1261.5	1245.0	1180.4	1118.6	1059.5	1026.5	1004.5	982.6	966.1	960.6
25°	1225.8	1210.7	1170.8	1114.5	1038.9	999.0	970.2	941.3	929.0	918.0	905.6
27.5°	1174.9	1137.8	1110.4	1036.1	989.4	944.1	915.2	893.2	878.1	867.1	857.5
30°	1111.7	1077.4	1038.9	977.1	934.5	891.9	865.7	847.9	831.4	824.5	816.3
32.5°	1045.8	1014.2	977.1	927.6	875.4	842.4	821.8	802.5	791.5	784.7	775.0
35°	986.7	946.8	922.1	875.4	832.8	795.7	776.4	759.9	747.6	744.8	743.4
37.5°	923.5	893.2	869.9	821.8	786.0	754.4	736.6	718.7	711.8	710.5	705.0
40°	868.5	842.4	820.4	775.0	736.6	707.7	694.0	683.0	676.1	676.1	674.7
42.5°	820.4	792.9	770.9	729.7	695.3	669.2	654.1	643.1	640.4	641.8	640.4
45°	766.8	743.4	721.5	678.9	650.0	630.8	614.3	608.8	604.6	606.0	607.4
47.5°	716.0	696.7	674.7	640.4	607.4	586.8	577.2	571.7	571.7	571.7	574.4
50°	670.6	648.6	629.4	593.7	563.4	546.9	538.7	531.8	533.2	534.6	535.9
52.5°	617.0	597.8	584.0	548.3	526.3	505.7	496.1	497.5	496.1	496.1	498.8
55°	570.3	551.1	537.3	504.3	482.3	468.6	460.4	456.2	457.6	454.9	460.4
57.5°	518.1	501.6	492.0	460.4	441.1	428.7	421.9	415.0	417.8	416.4	415.0
60°	472.7	453.5	438.4	416.4	399.9	384.8	380.7	373.8	376.5	373.8	372.4
62.5°	420.5	405.4	394.4	372.4	358.7	346.3	336.7	332.6	331.2	327.1	322.9
65°	368.3	360.0	349.0	327.1	313.3	303.7	298.2	294.1	292.7	281.7	269.3
67.5°	320.2	314.7	303.7	287.2	274.8	265.2	257.0	250.1	241.9	233.6	226.7
70°	274.8	266.6	259.7	244.6	233.6	224.0	215.7	207.5	203.4	195.1	192.4
72.5°	230.9	222.6	215.7	202.0	192.4	182.8	180.0	170.4	166.3	164.9	164.9
75°	185.5	178.6	174.5	162.2	153.9	147.0	142.9	140.2	137.4	134.7	130.5
77.5°	141.5	137.4	134.7	126.4	119.6	115.4	114.1	104.4	101.7	98.9	96.2
80°	103.1	101.7	98.9	92.1	89.3	79.7	79.7	77.0	75.6	75.6	75.6
82.5°	70.1	67.3	66.0	59.1	57.7	56.3	55.0	53.6	55.0	53.6	55.0
85°	37.1	35.7	34.4	34.4	34.4	34.4	34.4	34.4	34.4	33.0	34.4
87.5°	13.7	13.7	13.7	13.7	12.4	13.7	13.7	12.4	13.7	13.7	13.7
90°	6.1	6.1	6.1	10.7	10.7	12.2	13.7	13.0	13.7	14.5	15.3
92.5°	48.9	58.8	68.7	116.1	190.2	262.0	299.4	249.0	184.1	137.5	108.5
95°	63.4	79.4	95.5	161.9	287.2	469.7	622.5	640.0	566.0	447.6	345.2
97.5°	74.1	87.8	101.6	154.3	262.0	449.9	666.0	802.7	815.0	756.1	672.1
100°	87.1	99.3	111.5	156.6	242.9	398.7	614.1	809.6	921.1	936.4	899.0
102.5°	101.6	113.0	124.5	164.2	237.5	364.3	549.2	752.3	915.8	1006.7	1029.6
105°	118.4	129.4	140.5	177.2	240.6	347.5	501.0	680.5	855.4	987.6	1063.2
107.5°	135.2	146.2	157.3	190.9	249.8	342.9	469.7	621.7	781.3	924.2	1029.6
110°	152.8	163.1	173.4	207.0	260.4	344.5	455.2	579.7	715.7	847.8	958.5

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	169.6	179.9	190.2	222.3	271.9	349.0	448.3	556.0	667.5	780.6	883.7
115°	187.1	197.4	207.7	238.3	284.1	355.2	446.8	543.0	638.5	732.5	821.8
117.5°	203.2	213.9	224.6	253.6	296.3	361.3	446.0	536.2	621.7	701.2	773.7
120°	219.2	229.9	240.6	269.6	309.3	368.1	446.0	530.8	611.0	682.1	743.2
122.5°	235.2	245.6	255.9	284.9	321.6	375.0	445.3	524.7	601.9	669.8	724.1
125°	249.8	260.5	271.1	298.6	333.8	381.9	444.5	517.8	591.2	656.9	709.6
127.5°	263.5	274.2	284.9	311.6	344.5	387.2	443.0	508.7	578.9	642.3	695.0
130°	276.5	287.6	298.6	324.6	354.4	393.3	442.2	500.3	563.7	624.0	675.9
132.5°	288.7	299.0	309.3	335.3	364.3	398.7	441.5	492.6	547.6	603.4	653.8
135°	300.2	310.1	320.0	345.2	372.7	404.0	440.7	485.0	533.1	582.8	629.4
137.5°	310.1	319.6	329.2	352.9	378.8	407.1	440.7	478.1	519.4	562.9	603.4
140°	319.3	328.5	337.6	360.5	384.9	410.9	439.9	472.8	507.9	543.8	578.2
142.5°	327.7	336.4	345.2	367.4	389.5	414.0	439.9	468.2	497.2	527.8	556.0
145°	335.3	343.7	352.1	372.0	392.6	414.7	438.4	462.9	487.3	513.3	536.2
147.5°	342.9	350.5	358.2	377.3	395.6	415.5	436.1	458.3	478.9	500.3	519.4
150°	349.8	357.0	364.3	381.1	397.9	415.5	433.8	452.9	471.3	488.8	504.1
152.5°	356.7	363.2	369.7	384.2	399.5	414.0	430.0	446.8	462.9	477.4	491.1
155°	362.8	368.6	374.3	387.2	400.2	412.4	426.2	440.7	454.4	466.7	478.1
157.5°	368.9	373.5	378.1	389.5	400.2	410.9	422.4	434.6	445.3	456.0	465.9
160°	373.5	377.7	381.9	391.1	400.2	408.6	417.8	427.7	436.9	445.3	453.7
162.5°	378.1	381.2	384.2	392.6	400.2	406.3	413.2	421.6	428.5	435.4	441.5
165°	381.1	383.4	385.7	392.6	398.7	403.3	408.6	414.7	420.8	425.4	430.8
167.5°	383.4	385.3	387.2	392.6	397.2	400.2	404.0	408.6	413.2	417.0	421.6
170°	385.7	386.8	388.0	391.8	395.6	397.2	399.5	402.5	406.3	408.6	411.7
172.5°	387.2	388.0	388.8	391.1	394.1	394.1	394.9	397.2	400.2	401.7	403.3
175°	388.8	388.8	388.8	390.3	392.6	391.8	391.8	393.3	394.9	395.6	397.2
177.5°	388.8	388.8	388.8	389.5	391.1	389.5	389.5	390.3	391.1	391.8	391.8
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1611.9	1617.4	1610.6	1614.7	1605.1	1603.7	1605.1	1605.1	1606.4	1607.8	1609.2
5°	1521.2	1519.9	1511.6	1506.1	1502.0	1506.1	1508.9	1511.6	1508.9	1511.6	1513.0
7.5°	1436.0	1431.9	1427.8	1418.2	1420.9	1418.2	1426.4	1422.3	1422.3	1429.2	1434.7
10°	1360.5	1352.2	1349.5	1338.5	1330.2	1328.8	1338.5	1342.6	1346.7	1349.5	1360.5
12.5°	1262.9	1250.5	1240.9	1245.0	1221.7	1231.3	1234.0	1228.5	1245.0	1264.3	1253.3
15°	1158.4	1159.8	1140.6	1133.7	1114.5	1120.0	1121.3	1135.1	1148.8	1147.5	1163.9
17.5°	1081.5	1073.2	1056.8	1055.4	1047.1	1051.3	1049.9	1060.9	1056.8	1063.6	1077.4
20°	1010.0	1004.5	990.8	985.3	988.0	985.3	986.7	988.0	992.2	1007.3	1004.5
22.5°	953.7	946.8	946.8	940.0	931.7	929.0	935.8	940.0	945.4	948.2	955.1
25°	904.2	898.7	891.9	887.7	880.9	882.2	886.4	891.9	896.0	901.5	907.0
27.5°	853.4	853.4	846.5	845.1	842.4	841.0	846.5	849.3	849.3	853.4	858.9
30°	813.5	813.5	806.7	805.3	803.9	803.9	808.0	809.4	810.8	814.9	817.6
32.5°	775.0	773.7	770.9	772.3	770.9	772.3	772.3	773.7	776.4	777.8	783.3
35°	739.3	740.7	737.9	737.9	736.6	737.9	740.7	742.1	743.4	746.2	746.2
37.5°	705.0	707.7	706.3	710.5	710.5	710.5	710.5	713.2	713.2	713.2	711.8
40°	674.7	674.7	673.4	676.1	678.9	678.9	680.2	680.2	681.6	681.6	680.2
42.5°	640.4	643.1	647.2	648.6	651.4	650.0	654.1	652.7	654.1	651.4	648.6
45°	608.8	608.8	614.3	619.8	621.1	621.1	621.1	623.9	621.1	617.0	615.6
47.5°	574.4	577.2	579.9	586.8	588.2	588.2	588.2	588.2	585.4	585.4	585.4
50°	540.1	541.4	542.8	545.6	549.7	548.3	548.3	548.3	553.8	548.3	549.7
52.5°	498.8	500.2	501.6	507.1	505.7	505.7	507.1	507.1	511.2	509.8	507.1
55°	457.6	457.6	460.4	460.4	460.4	463.1	464.5	467.2	465.9	467.2	468.6
57.5°	416.4	413.6	412.3	412.3	416.4	415.0	416.4	416.4	421.9	424.6	426.0
60°	368.3	368.3	366.9	358.7	358.7	357.3	361.4	364.2	366.9	379.3	377.9
62.5°	318.8	313.3	307.8	309.2	300.9	305.1	302.3	305.1	313.3	322.9	324.3
65°	269.3	265.2	259.7	258.3	255.6	259.7	258.3	259.7	263.8	269.3	276.2
67.5°	225.4	224.0	221.2	219.9	219.9	219.9	222.6	222.6	224.0	228.1	232.2
70°	192.4	191.0	192.4	189.6	191.0	189.6	191.0	192.4	193.8	195.1	199.3
72.5°	162.2	162.2	162.2	159.4	162.2	160.8	160.8	162.2	163.5	164.9	167.7
75°	129.2	126.4	123.7	120.9	119.6	122.3	123.7	122.3	126.4	131.9	131.9
77.5°	97.6	96.2	96.2	96.2	97.6	96.2	98.9	97.6	98.9	98.9	101.7
80°	75.6	74.2	75.6	75.6	74.2	77.0	75.6	75.6	77.0	78.3	77.0
82.5°	55.0	56.3	55.0	55.0	55.0	57.7	55.0	55.0	55.0	56.3	56.3
85°	34.4	34.4	34.4	34.4	35.7	34.4	35.7	34.4	37.1	35.7	35.7
87.5°	12.4	13.7	15.1	15.1	15.1	15.1	13.7	15.1	16.5	15.1	16.5
90°	15.3	15.3	16.0	16.8	16.0	16.0	16.0	16.8	16.0	15.3	15.3
92.5°	99.0	89.4	77.9	72.6	69.5	69.5	69.5	72.6	77.9	89.4	99.0
95°	308.2	271.1	233.7	210.0	196.3	186.4	196.3	210.0	233.7	271.1	308.2
97.5°	629.4	586.6	534.6	488.8	465.9	447.6	465.9	488.8	534.6	586.6	629.4
100°	870.8	842.5	776.0	729.4	706.5	700.4	706.5	729.4	776.0	842.5	870.8
102.5°	1022.0	1014.3	979.9	949.4	924.9	920.4	924.9	949.4	979.9	1014.3	1022.0
105°	1078.8	1094.5	1096.0	1089.9	1079.2	1074.6	1079.2	1089.9	1096.0	1094.5	1078.8
107.5°	1061.6	1093.7	1127.3	1141.1	1147.2	1148.0	1147.2	1141.1	1127.3	1093.7	1061.6
110°	1000.6	1042.6	1096.8	1128.9	1142.6	1149.5	1142.6	1128.9	1096.8	1042.6	1000.6

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	925.7	967.7	1031.1	1071.6	1092.2	1104.4	1092.2	1071.6	1031.1	967.7	925.7
115°	858.5	895.2	955.5	1001.3	1025.8	1031.9	1025.8	1001.3	955.5	895.2	858.5
117.5°	805.8	837.9	891.3	931.0	957.0	960.8	957.0	931.0	891.3	837.9	805.8
120°	770.3	797.4	840.9	874.5	894.4	902.8	894.4	874.5	840.9	797.4	770.3
122.5°	747.0	769.9	805.0	832.5	848.6	857.0	848.6	832.5	805.0	769.9	747.0
125°	730.6	751.6	782.1	804.3	818.8	823.4	818.8	804.3	782.1	751.6	730.6
127.5°	714.9	734.8	765.3	785.2	797.4	802.0	797.4	785.2	765.3	734.8	714.9
130°	696.2	716.4	747.7	766.8	779.1	783.6	779.1	766.8	747.7	716.4	696.2
132.5°	674.0	694.3	724.8	747.0	758.4	763.0	758.4	747.0	724.8	694.3	674.0
135°	648.4	667.5	698.1	719.5	731.7	736.3	731.7	719.5	698.1	667.5	648.4
137.5°	621.0	638.5	667.5	689.7	699.6	705.0	699.6	689.7	667.5	638.5	621.0
140°	594.2	610.3	637.0	653.8	664.5	670.6	664.5	653.8	637.0	610.3	594.2
142.5°	569.4	582.8	605.7	621.0	630.1	633.9	630.1	621.0	605.7	582.8	569.4
145°	546.9	557.6	576.7	589.6	597.3	601.1	597.3	589.6	576.7	557.6	546.9
147.5°	528.2	536.9	551.4	562.9	569.0	570.5	569.0	562.9	551.4	536.9	528.2
150°	511.0	517.8	530.1	540.0	544.6	545.3	544.6	540.0	530.1	517.8	511.0
152.5°	496.4	501.8	511.7	519.4	521.7	522.4	521.7	519.4	511.7	501.8	496.4
155°	482.7	487.3	494.9	501.0	503.3	503.3	503.3	501.0	494.9	487.3	482.7
157.5°	469.7	473.5	479.7	484.2	485.8	485.8	485.8	484.2	479.7	473.5	469.7
160°	456.8	459.8	464.4	469.0	469.7	469.7	469.7	469.0	464.4	459.8	456.8
162.5°	444.2	446.8	449.9	454.4	455.2	454.4	455.2	454.4	449.9	446.8	444.2
165°	432.7	434.6	437.6	440.7	439.9	439.2	439.9	440.7	437.6	434.6	432.7
167.5°	422.8	423.9	425.4	427.7	427.7	427.0	427.7	427.7	425.4	423.9	422.8
170°	412.8	414.0	415.5	416.3	415.5	415.5	415.5	416.3	415.5	414.0	412.8
172.5°	404.0	404.8	405.6	406.3	405.6	404.0	405.6	406.3	405.6	404.8	404.0
175°	397.2	397.2	397.2	398.7	397.2	395.6	397.2	398.7	397.2	397.2	397.2
177.5°	392.2	392.6	391.8	392.6	391.1	389.5	391.1	392.6	391.8	392.6	392.2
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4	1705.4
2.5°	1614.7	1621.6	1618.8	1609.2	1613.3	1621.6	1629.8	1640.8	1647.7	1653.2	1655.9
5°	1519.9	1532.2	1529.5	1529.5	1535.0	1548.7	1562.5	1585.8	1594.1	1603.7	1617.4
7.5°	1436.0	1445.7	1453.9	1456.6	1464.9	1482.8	1500.6	1526.7	1547.3	1558.3	1566.6
10°	1361.8	1368.7	1381.1	1387.9	1396.2	1418.2	1444.3	1471.8	1492.4	1511.6	1522.6
12.5°	1267.0	1294.5	1311.0	1322.0	1333.0	1366.0	1386.6	1416.8	1441.5	1459.4	1475.9
15°	1161.2	1194.2	1203.8	1246.4	1273.9	1300.0	1331.6	1367.3	1390.7	1411.3	1433.3
17.5°	1071.9	1095.2	1106.2	1151.6	1174.9	1216.2	1261.5	1306.9	1342.6	1357.7	1379.7
20°	1015.5	1027.9	1049.9	1065.0	1089.7	1137.8	1187.3	1242.3	1295.9	1311.0	1333.0
22.5°	957.8	974.3	989.4	1010.0	1029.3	1062.3	1111.7	1172.2	1229.9	1257.4	1283.5
25°	905.6	922.1	931.7	953.7	971.6	1004.5	1038.9	1100.7	1169.4	1192.8	1234.0
27.5°	864.4	874.0	890.5	900.1	920.7	950.9	982.6	1029.3	1096.6	1136.5	1176.3
30°	823.1	830.0	843.8	857.5	872.6	893.2	929.0	974.3	1036.1	1070.5	1110.4
32.5°	781.9	792.9	801.2	810.8	827.3	852.0	876.7	920.7	970.2	1008.7	1048.5
35°	747.6	751.7	762.7	773.7	784.7	806.7	832.8	875.4	919.3	949.6	985.3
37.5°	710.5	717.3	725.6	729.7	747.6	761.3	788.8	821.8	874.0	893.2	929.0
40°	681.6	680.2	688.5	695.3	703.6	725.6	742.1	777.8	819.0	849.3	871.2
42.5°	645.9	645.9	648.6	656.9	667.9	681.6	700.8	731.1	773.7	795.7	821.8
45°	617.0	612.9	614.3	619.8	626.6	640.4	659.6	685.7	728.3	746.2	773.7
47.5°	582.7	578.5	578.5	584.0	589.5	599.2	614.3	644.5	678.9	702.2	722.8
50°	544.2	545.6	544.2	548.3	551.1	560.7	577.2	601.9	633.5	652.7	676.1
52.5°	508.5	505.7	504.3	507.1	512.6	519.4	537.3	559.3	589.5	608.8	629.4
55°	464.5	467.2	467.2	467.2	475.5	478.2	492.0	514.0	544.2	559.3	578.5
57.5°	424.6	423.3	426.0	424.6	431.5	441.1	452.1	468.6	498.8	514.0	531.8
60°	380.7	382.0	383.4	383.4	388.9	398.5	410.9	426.0	450.7	465.9	482.3
62.5°	327.1	333.9	340.8	343.5	351.8	358.7	366.9	383.4	405.4	416.4	431.5
65°	276.2	285.8	295.5	302.3	307.8	314.7	325.7	340.8	358.7	369.7	384.8
67.5°	232.2	239.1	251.5	258.3	269.3	277.6	284.5	296.8	318.8	322.9	335.3
70°	200.6	203.4	208.9	214.4	226.7	233.6	241.9	254.2	270.7	280.3	287.2
72.5°	169.0	170.4	173.1	178.6	184.1	192.4	202.0	213.0	228.1	232.2	241.9
75°	134.7	142.9	142.9	147.0	151.2	155.3	163.5	174.5	184.1	191.0	196.5
77.5°	100.3	104.4	107.2	114.1	119.6	123.7	129.2	137.4	142.9	148.4	152.5
80°	78.3	79.7	81.1	81.1	83.8	89.3	94.8	100.3	107.2	109.9	114.1
82.5°	57.7	57.7	57.7	60.5	61.8	63.2	63.2	66.0	72.8	75.6	79.7
85°	37.1	37.1	37.1	37.1	38.5	39.9	41.2	42.6	42.6	42.6	45.3
87.5°	15.1	17.9	16.5	17.9	17.9	17.9	17.9	19.2	19.2	20.6	20.6
90°	15.3	14.5	13.7	13.0	13.7	12.2	10.7	10.7	6.1	6.1	6.1
92.5°	108.5	137.5	184.1	249.0	299.4	262.0	190.2	116.1	68.7	58.8	48.9
95°	345.2	447.6	566.0	640.0	622.5	469.7	287.2	161.9	95.5	79.4	63.4
97.5°	672.1	756.1	815.0	802.7	666.0	449.9	262.0	154.3	101.6	87.8	74.1
100°	899.0	936.4	921.1	809.6	614.1	398.7	242.9	156.6	111.5	99.3	87.1
102.5°	1029.6	1006.7	915.8	752.3	549.2	364.3	237.5	164.2	124.5	113.0	101.6
105°	1063.2	987.6	855.4	680.5	501.0	347.5	240.6	177.2	140.5	129.4	118.4
107.5°	1029.6	924.2	781.3	621.7	469.7	342.9	249.8	190.9	157.3	146.2	135.2
110°	958.5	847.8	715.7	579.7	455.2	344.5	260.4	207.0	173.4	163.1	152.8

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	883.7	780.6	667.5	556.0	448.3	349.0	271.9	222.3	190.2	179.9	169.6
115°	821.8	732.5	638.5	543.0	446.8	355.2	284.1	238.3	207.7	197.4	187.1
117.5°	773.7	701.2	621.7	536.2	446.0	361.3	296.3	253.6	224.6	213.9	203.2
120°	743.2	682.1	611.0	530.8	446.0	368.1	309.3	269.6	240.6	229.9	219.2
122.5°	724.1	669.8	601.9	524.7	445.3	375.0	321.6	284.9	255.9	245.6	235.2
125°	709.6	656.9	591.2	517.8	444.5	381.9	333.8	298.6	271.1	260.5	249.8
127.5°	695.0	642.3	578.9	508.7	443.0	387.2	344.5	311.6	284.9	274.2	263.5
130°	675.9	624.0	563.7	500.3	442.2	393.3	354.4	324.6	298.6	287.6	276.5
132.5°	653.8	603.4	547.6	492.6	441.5	398.7	364.3	335.3	309.3	299.0	288.7
135°	629.4	582.8	533.1	485.0	440.7	404.0	372.7	345.2	320.0	310.1	300.2
137.5°	603.4	562.9	519.4	478.1	440.7	407.1	378.8	352.9	329.2	319.6	310.1
140°	578.2	543.8	507.9	472.8	439.9	410.9	384.9	360.5	337.6	328.5	319.3
142.5°	556.0	527.8	497.2	468.2	439.9	414.0	389.5	367.4	345.2	336.4	327.7
145°	536.2	513.3	487.3	462.9	438.4	414.7	392.6	372.0	352.1	343.7	335.3
147.5°	519.4	500.3	478.9	458.3	436.1	415.5	395.6	377.3	358.2	350.5	342.9
150°	504.1	488.8	471.3	452.9	433.8	415.5	397.9	381.1	364.3	357.0	349.8
152.5°	491.1	477.4	462.9	446.8	430.0	414.0	399.5	384.2	369.7	363.2	356.7
155°	478.1	466.7	454.4	440.7	426.2	412.4	400.2	387.2	374.3	368.6	362.8
157.5°	465.9	456.0	445.3	434.6	422.4	410.9	400.2	389.5	378.1	373.5	368.9
160°	453.7	445.3	436.9	427.7	417.8	408.6	400.2	391.1	381.9	377.7	373.5
162.5°	441.5	435.4	428.5	421.6	413.2	406.3	400.2	392.6	384.2	381.2	378.1
165°	430.8	425.4	420.8	414.7	408.6	403.3	398.7	392.6	385.7	383.4	381.1
167.5°	421.6	417.0	413.2	408.6	404.0	400.2	397.2	392.6	387.2	385.3	383.4
170°	411.7	408.6	406.3	402.5	399.5	397.2	395.6	391.8	388.0	386.8	385.7
172.5°	403.3	401.7	400.2	397.2	394.9	394.1	394.1	391.1	388.8	388.0	387.2
175°	397.2	395.6	394.9	393.3	391.8	391.8	392.6	390.3	388.8	388.8	388.8
177.5°	391.8	391.8	391.1	390.3	389.5	389.5	391.1	389.5	388.8	388.8	388.8
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1705.4	1705.4	1705.4	1705.4
2.5°	1666.9	1675.1	1688.9	1708.1
5°	1628.4	1651.8	1673.8	1702.6
7.5°	1594.1	1621.6	1651.8	1693.0
10°	1554.2	1588.6	1627.1	1677.9
12.5°	1507.5	1555.6	1599.6	1654.5
15°	1473.1	1508.9	1565.2	1629.8
17.5°	1425.0	1473.1	1529.5	1602.3
20°	1379.7	1430.5	1493.8	1569.3
22.5°	1331.6	1389.3	1452.5	1533.6
25°	1282.1	1344.0	1407.2	1493.8
27.5°	1236.8	1293.1	1364.6	1452.5
30°	1181.8	1246.4	1315.1	1407.2
32.5°	1128.2	1195.6	1265.6	1357.7
35°	1070.5	1137.8	1214.8	1302.7
37.5°	1014.2	1088.4	1158.4	1243.6
40°	952.3	1029.3	1102.1	1188.7
42.5°	891.9	971.6	1044.4	1118.6
45°	835.5	913.8	979.8	1049.9
47.5°	781.9	852.0	919.3	982.6
50°	729.7	788.8	850.6	902.8
52.5°	674.7	731.1	780.5	827.3
55°	625.3	669.2	713.2	755.8
57.5°	566.2	610.1	648.6	681.6
60°	516.7	544.2	581.3	615.6
62.5°	460.4	492.0	520.8	542.8
65°	405.4	432.9	454.9	474.1
67.5°	358.7	375.2	391.6	412.3
70°	302.3	316.1	335.3	350.4
72.5°	254.2	265.2	274.8	292.7
75°	206.1	215.7	221.2	237.7
77.5°	159.4	169.0	173.1	182.8
80°	122.3	123.7	129.2	137.4
82.5°	83.8	86.6	87.9	94.8
85°	48.1	55.0	53.6	56.3
87.5°	20.6	22.0	24.7	27.5
90°	5.3	4.6	2.3	0.8
92.5°	35.1	23.7	15.3	10.7
95°	45.1	35.1	27.5	25.2
97.5°	58.0	48.9	42.0	42.0
100°	72.6	63.4	58.0	58.0
102.5°	87.8	79.4	74.9	73.3
105°	104.6	95.5	91.7	89.4
107.5°	122.2	112.3	108.5	106.9
110°	139.0	129.8	126.0	124.5

TEST NUMBER: P1026057

CATALOG NUMBER: S124RDIP-B1020D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	155.8	147.4	142.8	141.3
115°	172.6	165.0	159.6	157.3
117.5°	189.4	181.0	176.4	174.1
120°	206.2	197.8	192.5	190.9
122.5°	220.7	213.1	207.7	206.2
125°	235.2	226.8	222.3	219.2
127.5°	248.2	239.1	233.7	231.4
130°	262.0	250.5	244.4	241.4
132.5°	272.7	262.0	253.6	251.3
135°	284.1	271.1	263.5	260.4
137.5°	293.3	281.1	272.7	269.6
140°	303.2	290.2	281.8	279.5
142.5°	312.4	300.2	292.5	290.2
145°	320.8	310.1	302.5	300.2
147.5°	330.7	319.3	312.4	311.6
150°	338.4	329.2	323.1	322.3
152.5°	346.8	338.4	332.2	332.2
155°	354.4	346.8	342.2	341.4
157.5°	361.3	355.2	350.6	350.6
160°	367.4	362.0	359.0	359.0
162.5°	372.7	368.1	365.9	366.6
165°	377.3	373.5	372.0	372.0
167.5°	381.1	378.1	377.3	378.1
170°	384.2	381.9	381.1	381.9
172.5°	386.5	384.9	384.9	385.7
175°	388.0	387.2	387.2	388.0
177.5°	388.8	388.0	388.8	389.5
180°	388.8	388.8	388.8	388.8

(END OF REPORT)