

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026075

Luminaire Tested: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026075
REPORT IS A COMBINATION OF REPORTS P999015 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6870.0 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66
1	101	97	93	89	94	90	87	84	79	77	74	69	67	65	59	58	57
2	92	85	79	74	86	80	75	70	70	66	63	61	58	55	53	50	49
3	84	75	68	62	79	71	64	59	62	57	53	54	51	47	47	44	42
4	77	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	37
5	71	60	52	46	67	56	49	44	50	44	40	44	39	36	38	35	32
6	66	54	46	40	62	51	44	38	45	39	35	40	35	32	35	31	28
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	24	21
10	50	37	30	25	46	36	29	25	32	26	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13374	13374	13374	13374
5°	13375	15113	13396	11551
10°	13303	17421	13293	10045
15°	13144	19606	13144	8410
20°	12979	21258	12911	7406
25°	12777	21349	12718	6689
30°	12561	18153	12463	6196
35°	12258	13697	12102	5828
40°	11919	9926	11685	5541
45°	11360	7544	11078	5287
50°	10697	6097	10403	4915
55°	9978	5049	9651	4420
60°	9256	4269	8842	3675
65°	8351	3478	8083	2921
70°	7518	2819	7164	2373
75°	6588	2032	6132	1739
80°	5437	1347	4948	1278
85°	3944	692	3267	692

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 16743 cd/sqm

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.8	2.3
10°-20°	479.6	7.0
20°-30°	751.2	10.9
30°-40°	834.2	12.1
40°-50°	739.2	10.8
50°-60°	576.1	8.4
60°-70°	376.8	5.5
70°-80°	184.9	2.7
80°-90°	46.5	0.7
90°-100°	270.9	3.9
100°-110°	565.6	8.2
110°-120°	502.8	7.3
120°-130°	423.2	6.2
130°-140°	353.1	5.1
140°-150°	269.6	3.9
150°-160°	189.5	2.8
160°-170°	111.5	1.6
170°-180°	36.3	0.5
0°-30°	1389.6	20.2
0°-40°	2223.9	32.4
0°-60°	3539.2	51.5
0°-90°	4147.5	60.4
90°-120°	1339.3	19.5
90°-150°	2385.3	34.7
90°-180°	2723.0	39.6
0°-180°	6870.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1640	1640	1640	1640	1640	
5°	1638	1895	1640	1448	1638	156
15°	1567	2511	1567	1077	1567	442
25°	1437	2708	1430	848	1437	662
35°	1253	1668	1237	710	1253	783
45°	1010	852	985	597	1010	779
55°	727	509	703	445	727	650
65°	456	297	441	250	456	455
75°	229	137	213	118	229	243
85°	54	33	45	33	54	61
90°	1	15	1	15	1	5
95°	24	179	24	179	24	27
105°	86	1033	86	1033	86	92
115°	151	992	151	992	151	150
125°	211	792	211	792	211	188
135°	250	708	250	708	250	194
145°	289	578	289	578	289	181
155°	328	484	328	484	328	151
165°	358	422	358	422	358	101
175°	373	380	373	380	373	35
180°	374	374	374	374	374	

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1
2.5°	1642.8	1657.3	1665.2	1671.8	1685.0	1690.3	1700.9	1703.5	1714.1	1712.8	1708.8
5°	1637.5	1662.6	1681.1	1700.9	1724.7	1737.9	1752.4	1773.6	1784.2	1798.7	1808.0
7.5°	1628.2	1662.6	1693.0	1723.4	1761.7	1782.8	1801.3	1834.4	1862.1	1885.9	1912.4
10°	1613.7	1657.3	1702.2	1743.2	1796.1	1821.2	1848.9	1897.8	1936.1	1969.2	2011.5
12.5°	1591.2	1652.0	1702.2	1757.7	1825.1	1859.5	1896.5	1954.6	1999.6	2053.8	2106.6
15°	1567.4	1634.8	1700.9	1773.6	1850.2	1889.9	1926.9	2004.9	2073.6	2135.7	2193.9
17.5°	1541.0	1615.0	1687.7	1768.3	1860.8	1909.7	1953.3	2047.2	2122.5	2203.1	2261.3
20°	1509.3	1589.9	1673.1	1763.0	1867.4	1921.6	1970.5	2077.6	2160.8	2248.0	2320.7
22.5°	1474.9	1562.1	1653.3	1751.1	1859.5	1919.0	1975.8	2090.8	2187.3	2267.9	2365.7
25°	1436.6	1529.1	1622.9	1726.0	1847.6	1912.4	1970.5	2084.2	2187.3	2293.0	2388.1
27.5°	1396.9	1492.1	1589.9	1698.3	1822.5	1885.9	1952.0	2061.7	2182.0	2296.9	2393.4
30°	1353.3	1445.8	1548.9	1652.0	1784.2	1847.6	1915.0	2033.9	2164.8	2279.8	2384.2
32.5°	1305.7	1400.9	1498.7	1605.7	1735.3	1804.0	1866.1	2000.9	2134.4	2248.0	2345.8
35°	1252.9	1342.7	1435.3	1545.0	1673.1	1735.3	1809.3	1949.4	2084.2	2204.4	2267.9
37.5°	1196.0	1282.0	1367.9	1476.2	1599.1	1674.5	1747.2	1888.6	2031.3	2111.9	2145.0
40°	1143.2	1218.5	1293.8	1398.3	1522.5	1600.5	1674.5	1821.2	1946.7	2008.8	1983.7
42.5°	1075.8	1153.8	1221.2	1317.6	1443.2	1515.9	1591.2	1743.2	1845.0	1870.1	1808.0
45°	1009.7	1074.5	1139.2	1233.1	1365.2	1427.3	1507.9	1649.4	1733.9	1711.5	1620.3
47.5°	944.9	997.8	1058.6	1149.8	1268.7	1342.7	1418.1	1541.0	1600.5	1568.7	1441.9
50°	868.3	921.2	984.6	1063.9	1178.9	1250.2	1309.7	1423.4	1468.3	1390.3	1237.0
52.5°	795.6	841.9	896.0	970.1	1079.7	1144.5	1209.3	1307.1	1321.6	1231.7	1070.5
55°	726.9	763.9	820.7	880.2	980.6	1049.4	1094.3	1177.5	1173.6	1061.2	922.5
57.5°	655.5	689.9	728.2	790.3	885.5	937.0	985.9	1058.6	1020.3	925.1	787.7
60°	592.1	611.9	650.2	709.7	790.3	835.3	873.6	913.2	880.2	777.1	671.4
62.5°	522.0	544.5	572.3	619.8	691.2	733.5	761.2	778.4	744.1	664.8	568.3
65°	456.0	475.8	504.9	547.1	601.3	633.0	647.6	659.5	641.0	551.1	474.5
67.5°	396.5	409.7	436.1	463.9	522.0	530.0	549.8	555.1	518.1	449.3	388.6
70°	337.0	350.2	362.1	395.2	421.6	436.1	440.1	440.1	403.1	358.2	307.9
72.5°	281.5	289.4	301.3	323.8	338.3	348.9	354.2	347.6	313.2	276.2	239.2
75°	228.6	232.6	243.2	257.7	269.6	265.6	264.3	256.4	231.3	204.8	183.7
77.5°	175.8	178.4	190.3	194.3	194.3	198.2	193.0	185.0	163.9	144.1	134.8
80°	132.2	136.1	137.4	140.1	137.4	137.4	133.5	120.3	109.7	100.4	93.8
82.5°	91.2	93.8	95.2	91.2	93.8	89.9	83.3	74.0	67.4	66.1	63.4
85°	54.2	55.5	54.2	54.2	50.2	48.9	43.6	42.3	39.6	39.6	38.3
87.5°	26.4	25.1	22.5	19.8	19.8	18.5	19.8	17.2	19.8	18.5	17.2
90°	0.7	2.2	4.4	5.1	5.9	5.9	5.9	10.3	10.3	11.8	13.2
92.5°	10.3	14.7	22.8	33.8	47.0	56.6	66.1	111.6	182.9	251.9	287.9
95°	24.2	26.4	33.8	43.3	61.0	76.4	91.8	155.7	276.1	451.7	598.5
97.5°	40.4	40.4	47.0	55.8	71.2	84.4	97.7	148.3	251.9	432.6	640.4
100°	55.8	55.8	61.0	69.8	83.7	95.4	107.2	150.6	233.5	383.4	590.5
102.5°	70.5	72.0	76.4	84.5	97.7	108.7	119.7	157.9	228.4	350.3	528.0
105°	85.9	88.1	91.8	100.6	113.8	124.4	135.1	170.4	231.3	334.1	481.8
107.5°	102.8	104.3	108.0	117.5	130.0	140.6	151.3	183.6	240.1	329.7	451.7
110°	119.7	121.2	124.8	133.7	146.9	156.8	166.7	199.0	250.4	331.2	437.7

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	135.9	137.3	141.7	149.8	163.0	173.0	182.9	213.7	261.4	335.6	431.1
115°	151.3	153.5	158.6	166.0	179.9	189.9	199.8	229.1	273.2	341.5	429.6
117.5°	167.4	169.6	174.1	182.1	195.3	205.6	215.9	243.8	284.9	347.4	428.9
120°	183.6	185.1	190.2	198.3	210.8	221.0	231.3	259.2	297.4	354.0	428.9
122.5°	198.3	199.8	204.9	212.2	226.2	236.1	246.0	273.9	309.2	360.6	428.2
125°	210.8	213.7	218.1	226.2	240.1	250.4	260.7	287.1	320.9	367.2	427.4
127.5°	222.5	224.7	229.9	238.7	253.4	263.6	273.9	299.6	331.2	372.3	425.9
130°	232.1	235.0	240.9	251.9	265.9	276.5	287.1	312.1	340.8	378.2	425.2
132.5°	241.6	243.8	251.9	262.2	277.6	287.5	297.4	322.4	350.3	383.4	424.5
135°	250.4	253.4	260.7	273.2	288.6	298.2	307.7	331.9	358.4	388.5	423.7
137.5°	259.2	262.2	270.3	282.0	298.2	307.4	316.5	339.3	364.3	391.4	423.7
140°	268.8	271.0	279.1	291.6	307.0	315.8	324.6	346.6	370.1	395.1	423.0
142.5°	279.1	281.3	288.6	300.4	315.1	323.5	331.9	353.2	374.5	398.0	423.0
145°	288.6	290.8	298.2	308.4	322.4	330.5	338.6	357.7	377.5	398.8	421.5
147.5°	299.6	300.4	307.0	318.0	329.7	337.0	344.4	362.8	380.4	399.5	419.3
150°	309.9	310.6	316.5	325.3	336.4	343.4	350.3	366.5	382.6	399.5	417.1
152.5°	319.5	319.5	325.3	333.4	343.0	349.2	355.4	369.4	384.1	398.0	413.5
155°	328.3	329.0	333.4	340.8	348.8	354.4	359.9	372.3	384.8	396.6	409.8
157.5°	337.1	337.1	341.5	347.4	354.7	359.1	363.5	374.5	384.8	395.1	406.1
160°	345.2	345.2	348.1	353.2	359.1	363.2	367.2	376.0	384.8	392.9	401.7
162.5°	352.5	351.8	354.0	358.4	363.5	366.4	369.4	377.5	384.8	390.7	397.3
165°	357.7	357.7	359.1	362.8	366.5	368.7	370.9	377.5	383.4	387.8	392.9
167.5°	363.5	362.8	363.5	366.5	368.7	370.5	372.3	377.5	381.9	384.8	388.5
170°	367.2	366.5	367.2	369.4	370.9	372.0	373.1	376.7	380.4	381.9	384.1
172.5°	370.9	370.1	370.1	371.6	372.3	373.0	373.8	376.0	378.9	378.9	379.7
175°	373.1	372.3	372.3	373.1	373.8	373.8	373.8	375.3	377.5	376.7	376.7
177.5°	374.5	373.8	373.1	373.8	373.8	373.8	373.8	374.5	376.0	374.5	374.5
180°	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1
2.5°	1719.4	1733.9	1735.3	1748.5	1744.5	1737.9	1749.8	1741.9	1757.7	1752.4	1759.1
5°	1819.8	1839.7	1856.9	1867.4	1885.9	1882.0	1901.8	1895.2	1909.7	1895.2	1913.7
7.5°	1937.5	1970.5	1987.7	2015.4	2023.4	2024.7	2048.5	2053.8	2063.0	2053.8	2064.3
10°	2052.4	2092.1	2131.7	2154.2	2168.7	2188.6	2209.7	2219.0	2225.6	2216.3	2222.9
12.5°	2156.9	2219.0	2262.6	2307.5	2318.1	2335.3	2357.7	2355.1	2381.5	2376.2	2388.1
15°	2253.3	2322.1	2374.9	2410.6	2439.7	2454.2	2496.5	2499.1	2497.8	2511.0	2503.1
17.5°	2339.2	2397.4	2472.7	2519.0	2554.7	2554.7	2578.4	2627.3	2623.4	2622.1	2630.0
20°	2409.3	2475.4	2545.4	2623.4	2652.5	2657.7	2690.8	2715.9	2719.9	2719.9	2719.9
22.5°	2462.1	2540.1	2615.4	2671.0	2693.4	2711.9	2741.0	2756.9	2762.1	2759.5	2762.1
25°	2488.6	2562.6	2639.2	2689.5	2702.7	2713.2	2715.9	2725.1	2723.8	2708.0	2717.2
27.5°	2493.9	2565.2	2615.4	2628.7	2622.1	2615.4	2573.2	2577.1	2565.2	2541.4	2550.7
30°	2470.1	2508.4	2507.1	2466.1	2454.2	2426.5	2388.1	2331.3	2285.0	2265.2	2271.8
32.5°	2384.2	2384.2	2336.6	2244.1	2203.1	2152.9	2084.2	2032.6	1971.8	1958.6	1983.7
35°	2265.2	2197.8	2110.6	1989.0	1926.9	1889.9	1770.9	1733.9	1682.4	1667.9	1679.8
37.5°	2080.2	1967.9	1841.0	1727.3	1674.5	1608.4	1504.0	1451.1	1414.1	1389.0	1400.9
40°	1872.7	1736.6	1604.4	1464.3	1406.2	1352.0	1274.0	1226.4	1167.0	1169.6	1173.6
42.5°	1674.5	1514.6	1366.5	1237.0	1181.5	1136.6	1082.4	1024.2	1003.1	996.5	989.9
45°	1464.3	1293.8	1155.1	1058.6	1008.4	966.1	915.9	882.8	857.7	852.4	859.0
47.5°	1266.1	1122.0	989.9	900.0	859.0	837.9	798.2	767.9	752.0	738.8	746.7
50°	1086.4	951.6	845.8	770.5	741.4	726.9	689.9	674.0	658.2	654.2	652.9
52.5°	938.3	823.4	732.2	671.4	648.9	641.0	613.2	590.8	577.5	581.5	584.1
55°	803.5	705.7	634.4	585.5	567.0	557.7	537.9	522.0	512.8	508.8	511.5
57.5°	684.6	600.0	548.5	508.8	494.3	490.3	469.2	463.9	457.3	453.3	453.3
60°	576.2	516.7	469.2	446.7	430.8	426.9	411.0	404.4	403.1	399.1	396.5
62.5°	485.0	436.1	403.1	379.3	372.7	371.4	360.8	352.9	348.9	346.3	346.3
65°	405.7	370.0	342.3	325.1	319.8	317.2	305.3	302.6	300.0	297.4	296.0
67.5°	338.3	306.6	286.8	274.9	268.3	269.6	263.0	257.7	257.7	256.4	255.1
70°	273.6	253.7	236.6	230.0	227.3	224.7	222.0	218.1	216.7	216.7	216.7
72.5°	215.4	202.2	193.0	189.0	186.3	183.7	181.1	181.1	181.1	179.7	179.7
75°	165.2	159.9	153.3	149.3	149.3	152.0	148.0	144.1	140.1	137.4	138.8
77.5°	124.2	121.6	117.6	111.0	112.3	109.7	109.7	107.0	108.4	108.4	105.7
80°	91.2	87.2	85.9	81.9	83.3	81.9	80.6	80.6	78.0	78.0	78.0
82.5°	63.4	59.5	59.5	58.2	56.8	56.8	55.5	55.5	56.8	54.2	54.2
85°	38.3	37.0	37.0	34.4	34.4	34.4	34.4	35.7	34.4	33.0	33.0
87.5°	17.2	18.5	17.2	15.9	15.9	15.9	14.5	14.5	13.2	14.5	14.5
90°	12.5	13.2	14.0	14.7	14.7	14.7	15.4	16.2	15.4	15.4	15.4
92.5°	239.4	177.0	132.2	104.3	95.1	85.9	74.9	69.8	66.8	66.8	66.8
95°	615.4	544.2	430.4	331.9	296.3	260.7	224.7	202.0	188.7	179.2	188.7
97.5°	771.8	783.6	727.1	646.3	605.2	564.0	514.1	470.0	448.0	430.4	448.0
100°	778.5	885.7	900.4	864.4	837.2	810.0	746.1	701.3	679.3	673.4	679.3
102.5°	723.4	880.5	967.9	990.0	982.6	975.3	942.2	912.9	889.4	884.9	889.4
105°	654.3	822.5	949.6	1022.3	1037.4	1052.4	1053.9	1048.0	1037.7	1033.3	1037.7
107.5°	597.8	751.3	888.6	990.0	1020.8	1051.7	1084.0	1097.2	1103.1	1103.8	1103.1
110°	557.4	688.1	815.2	921.7	962.0	1002.4	1054.6	1085.4	1098.7	1105.3	1098.7

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	534.6	641.9	750.6	849.7	890.1	930.5	991.4	1030.4	1050.2	1061.9	1050.2
115°	522.2	614.0	704.3	790.2	825.4	860.7	918.7	962.8	986.3	992.2	986.3
117.5°	515.5	597.8	674.2	743.9	774.8	805.6	857.0	895.2	920.2	923.9	920.2
120°	510.4	587.5	655.8	714.6	740.7	766.7	808.6	840.9	860.0	868.1	860.0
122.5°	504.5	578.7	644.1	696.2	718.2	740.3	774.1	800.5	815.9	824.0	815.9
125°	497.9	568.4	631.6	682.3	702.4	722.6	752.0	773.3	787.3	791.7	787.3
127.5°	489.1	556.7	617.6	668.3	687.4	706.5	735.9	755.0	766.7	771.1	766.7
130°	481.0	542.0	600.0	649.9	669.4	688.9	719.0	737.3	749.1	753.5	749.1
132.5°	473.7	526.6	580.2	628.6	648.1	667.6	696.9	718.2	729.3	733.7	729.3
135°	466.3	512.6	560.3	605.1	623.5	641.9	671.2	691.8	703.5	708.0	703.5
137.5°	459.7	499.4	541.2	580.2	597.1	614.0	641.9	663.2	672.7	677.8	672.7
140°	454.6	488.4	522.9	555.9	571.3	586.8	612.5	628.6	638.9	644.8	638.9
142.5°	450.2	478.1	507.5	534.6	547.4	560.3	582.4	597.1	605.9	609.5	605.9
145°	445.0	468.5	493.5	515.5	525.8	536.1	554.5	567.0	574.3	578.0	574.3
147.5°	440.6	460.5	481.0	499.4	507.8	516.3	530.2	541.2	547.1	548.6	547.1
150°	435.5	453.1	470.0	484.7	491.3	497.9	509.7	519.2	523.6	524.4	523.6
152.5°	429.6	445.0	459.0	472.2	477.4	482.5	492.0	499.4	501.6	502.3	501.6
155°	423.7	437.0	448.7	459.7	464.1	468.5	475.9	481.8	484.0	484.0	484.0
157.5°	417.9	428.2	438.4	448.0	451.6	455.3	461.2	465.6	467.1	467.1	467.1
160°	411.3	420.1	428.2	436.2	439.2	442.1	446.5	450.9	451.7	451.7	451.7
162.5°	405.4	412.0	418.6	424.5	427.0	429.6	432.6	437.0	437.7	437.0	437.7
165°	398.8	404.7	409.1	414.2	416.0	417.9	420.8	423.7	423.0	422.3	423.0
167.5°	392.9	397.3	401.0	405.4	406.5	407.6	409.1	411.3	411.3	410.5	411.3
170°	387.0	390.7	392.9	395.8	396.9	398.0	399.5	400.2	399.5	399.5	399.5
172.5°	381.9	384.8	386.3	387.8	388.5	389.2	390.0	390.7	390.0	388.5	390.0
175°	378.2	379.7	380.4	381.9	381.9	381.9	381.9	383.4	381.9	380.4	381.9
177.5°	375.3	376.0	376.7	376.7	377.1	377.5	376.7	377.5	376.0	374.5	376.0
180°	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1
2.5°	1763.0	1753.8	1752.4	1752.4	1737.9	1745.8	1730.0	1712.8	1704.9	1704.9	1690.3
5°	1909.7	1900.5	1891.2	1876.7	1876.7	1868.7	1843.6	1818.5	1800.0	1784.2	1767.0
7.5°	2060.4	2051.1	2024.7	2010.2	2018.1	2002.2	1969.2	1926.9	1895.2	1870.1	1834.4
10°	2224.3	2199.1	2185.9	2178.0	2150.2	2133.1	2094.7	2032.6	1993.0	1959.9	1913.7
12.5°	2357.7	2365.7	2315.4	2319.4	2291.7	2267.9	2208.4	2148.9	2089.5	2043.2	1974.5
15°	2501.8	2478.0	2447.6	2423.8	2414.6	2385.5	2335.3	2256.0	2191.2	2118.5	2040.6
17.5°	2615.4	2596.9	2567.9	2545.4	2525.6	2455.5	2413.2	2343.2	2254.7	2183.3	2088.1
20°	2711.9	2694.7	2653.8	2639.2	2603.6	2553.3	2492.5	2384.2	2304.9	2226.9	2134.4
22.5°	2752.9	2735.7	2700.0	2681.5	2659.1	2610.2	2552.0	2448.9	2351.1	2253.3	2155.5
25°	2718.5	2718.5	2701.4	2694.7	2674.9	2631.3	2571.8	2484.6	2380.2	2274.5	2158.2
27.5°	2552.0	2585.1	2596.9	2603.6	2603.6	2604.9	2563.9	2479.3	2377.6	2274.5	2152.9
30°	2311.5	2367.0	2415.9	2430.4	2455.5	2483.3	2500.5	2459.5	2368.3	2259.9	2138.4
32.5°	2008.8	2080.2	2171.4	2193.9	2228.2	2311.5	2357.7	2374.9	2324.7	2229.5	2100.0
35°	1707.5	1797.4	1852.9	1921.6	1953.3	2076.2	2179.3	2241.4	2229.5	2172.7	2055.1
37.5°	1444.5	1496.1	1563.5	1636.1	1699.6	1817.2	1945.4	2065.7	2114.6	2086.8	1998.3
40°	1192.1	1252.9	1333.5	1393.0	1436.6	1554.2	1712.8	1843.6	1950.7	1967.9	1913.7
42.5°	1013.7	1074.5	1123.4	1188.1	1222.5	1336.1	1476.2	1640.1	1767.0	1834.4	1810.6
45°	876.2	913.2	952.9	989.9	1032.2	1132.6	1262.1	1441.9	1584.6	1679.8	1689.0
47.5°	756.0	789.0	823.4	857.7	881.5	959.5	1078.4	1225.1	1381.1	1511.9	1563.5
50°	671.4	687.2	712.3	732.2	759.9	827.3	922.5	1049.4	1214.6	1356.0	1423.4
52.5°	588.1	607.9	627.8	644.9	663.4	711.0	798.2	907.9	1050.7	1196.0	1279.3
55°	518.1	533.9	552.4	564.3	574.9	617.2	683.3	767.9	890.8	1028.2	1131.3
57.5°	461.2	467.8	483.7	490.3	502.2	536.6	584.1	659.5	758.6	892.1	976.7
60°	399.1	412.3	424.2	429.5	438.8	462.6	495.6	565.6	651.5	749.3	845.8
62.5°	348.9	354.2	363.4	370.0	376.7	401.8	429.5	482.4	547.1	629.1	717.6
65°	302.6	305.3	310.6	319.8	323.8	342.3	358.2	396.5	457.3	519.4	607.9
67.5°	255.1	257.7	264.3	269.6	273.6	285.5	302.6	330.4	363.4	432.2	481.1
70°	218.1	218.1	222.0	224.7	228.6	233.9	243.2	264.3	294.7	338.3	383.3
72.5°	182.4	182.4	182.4	186.3	186.3	190.3	195.6	210.1	231.3	265.6	294.7
75°	141.4	142.7	145.4	145.4	146.7	152.0	155.9	159.9	170.5	193.0	219.4
77.5°	107.0	109.7	111.0	108.4	111.0	111.0	116.3	121.6	126.9	133.5	153.3
80°	79.3	80.6	78.0	79.3	79.3	81.9	84.6	83.3	85.9	93.8	99.1
82.5°	52.9	54.2	54.2	54.2	54.2	58.2	58.2	56.8	58.2	59.5	60.8
85°	33.0	31.7	31.7	33.0	31.7	31.7	33.0	34.4	33.0	34.4	35.7
87.5°	14.5	14.5	14.5	14.5	13.2	13.2	14.5	13.2	14.5	13.2	11.9
90°	16.2	15.4	14.7	14.7	14.7	14.0	13.2	12.5	13.2	11.8	10.3
92.5°	69.8	74.9	85.9	95.1	104.3	132.2	177.0	239.4	287.9	251.9	182.9
95°	202.0	224.7	260.7	296.3	331.9	430.4	544.2	615.4	598.5	451.7	276.1
97.5°	470.0	514.1	564.0	605.2	646.3	727.1	783.6	771.8	640.4	432.6	251.9
100°	701.3	746.1	810.0	837.2	864.4	900.4	885.7	778.5	590.5	383.4	233.5
102.5°	912.9	942.2	975.3	982.6	990.0	967.9	880.5	723.4	528.0	350.3	228.4
105°	1048.0	1053.9	1052.4	1037.4	1022.3	949.6	822.5	654.3	481.8	334.1	231.3
107.5°	1097.2	1084.0	1051.7	1020.8	990.0	888.6	751.3	597.8	451.7	329.7	240.1
110°	1085.4	1054.6	1002.4	962.0	921.7	815.2	688.1	557.4	437.7	331.2	250.4

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1030.4	991.4	930.5	890.1	849.7	750.6	641.9	534.6	431.1	335.6	261.4
115°	962.8	918.7	860.7	825.4	790.2	704.3	614.0	522.2	429.6	341.5	273.2
117.5°	895.2	857.0	805.6	774.8	743.9	674.2	597.8	515.5	428.9	347.4	284.9
120°	840.9	808.6	766.7	740.7	714.6	655.8	587.5	510.4	428.9	354.0	297.4
122.5°	800.5	774.1	740.3	718.2	696.2	644.1	578.7	504.5	428.2	360.6	309.2
125°	773.3	752.0	722.6	702.4	682.3	631.6	568.4	497.9	427.4	367.2	320.9
127.5°	755.0	735.9	706.5	687.4	668.3	617.6	556.7	489.1	425.9	372.3	331.2
130°	737.3	719.0	688.9	669.4	649.9	600.0	542.0	481.0	425.2	378.2	340.8
132.5°	718.2	696.9	667.6	648.1	628.6	580.2	526.6	473.7	424.5	383.4	350.3
135°	691.8	671.2	641.9	623.5	605.1	560.3	512.6	466.3	423.7	388.5	358.4
137.5°	663.2	641.9	614.0	597.1	580.2	541.2	499.4	459.7	423.7	391.4	364.3
140°	628.6	612.5	586.8	571.3	555.9	522.9	488.4	454.6	423.0	395.1	370.1
142.5°	597.1	582.4	560.3	547.4	534.6	507.5	478.1	450.2	423.0	398.0	374.5
145°	567.0	554.5	536.1	525.8	515.5	493.5	468.5	445.0	421.5	398.8	377.5
147.5°	541.2	530.2	516.3	507.8	499.4	481.0	460.5	440.6	419.3	399.5	380.4
150°	519.2	509.7	497.9	491.3	484.7	470.0	453.1	435.5	417.1	399.5	382.6
152.5°	499.4	492.0	482.5	477.4	472.2	459.0	445.0	429.6	413.5	398.0	384.1
155°	481.8	475.9	468.5	464.1	459.7	448.7	437.0	423.7	409.8	396.6	384.8
157.5°	465.6	461.2	455.3	451.6	448.0	438.4	428.2	417.9	406.1	395.1	384.8
160°	450.9	446.5	442.1	439.2	436.2	428.2	420.1	411.3	401.7	392.9	384.8
162.5°	437.0	432.6	429.6	427.0	424.5	418.6	412.0	405.4	397.3	390.7	384.8
165°	423.7	420.8	417.9	416.0	414.2	409.1	404.7	398.8	392.9	387.8	383.4
167.5°	411.3	409.1	407.6	406.5	405.4	401.0	397.3	392.9	388.5	384.8	381.9
170°	400.2	399.5	398.0	396.9	395.8	392.9	390.7	387.0	384.1	381.9	380.4
172.5°	390.7	390.0	389.2	388.5	387.8	386.3	384.8	381.9	379.7	378.9	378.9
175°	383.4	381.9	381.9	381.9	381.9	380.4	379.7	378.2	376.7	376.7	377.5
177.5°	377.5	376.7	377.5	377.1	376.7	376.7	376.0	375.3	374.5	374.5	376.0
180°	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1
2.5°	1682.4	1675.8	1671.8	1670.5	1658.6	1652.0	1648.0	1645.4	1641.4	1630.9	1621.6
5°	1745.8	1727.3	1718.1	1707.5	1689.0	1667.9	1650.7	1640.1	1626.9	1605.7	1585.9
7.5°	1805.3	1777.6	1759.1	1744.5	1712.8	1678.4	1650.7	1628.2	1603.1	1574.0	1546.3
10°	1867.4	1822.5	1798.7	1776.2	1730.0	1685.0	1645.4	1612.4	1576.7	1538.3	1507.9
12.5°	1916.3	1856.9	1830.4	1798.7	1741.9	1689.0	1638.8	1593.9	1547.6	1506.6	1463.0
15°	1973.2	1899.1	1868.7	1827.8	1749.8	1681.1	1616.3	1567.4	1519.8	1459.0	1412.8
17.5°	2006.2	1920.3	1876.7	1841.0	1756.4	1673.1	1597.8	1537.0	1481.5	1420.7	1371.8
20°	2039.2	1941.4	1892.5	1842.3	1741.9	1653.3	1574.0	1501.3	1443.2	1377.1	1326.9
22.5°	2049.8	1936.1	1884.6	1838.3	1732.6	1633.5	1542.3	1468.3	1400.9	1334.8	1278.0
25°	2049.8	1934.8	1874.0	1814.6	1703.5	1601.8	1510.6	1430.0	1354.6	1288.6	1231.7
27.5°	2028.7	1908.4	1845.0	1790.8	1675.8	1566.1	1472.3	1383.7	1311.0	1244.9	1180.2
30°	2002.2	1870.1	1806.6	1741.9	1630.9	1526.5	1424.7	1342.7	1266.1	1190.8	1132.6
32.5°	1969.2	1829.1	1759.1	1693.0	1575.3	1467.0	1373.1	1292.5	1219.8	1141.9	1077.1
35°	1921.6	1768.3	1690.3	1632.2	1518.5	1406.2	1316.3	1237.0	1167.0	1086.4	1016.3
37.5°	1860.8	1712.8	1633.5	1562.1	1444.5	1341.4	1256.8	1180.2	1111.5	1037.5	959.5
40°	1789.4	1634.8	1566.1	1490.8	1366.5	1268.7	1189.4	1120.7	1052.0	982.0	906.6
42.5°	1708.8	1555.5	1478.9	1406.2	1287.2	1190.8	1116.8	1054.6	991.2	926.4	845.8
45°	1612.4	1468.3	1394.3	1325.6	1210.6	1111.5	1044.1	984.6	930.4	864.3	793.0
47.5°	1504.0	1378.4	1303.1	1229.1	1116.8	1030.8	964.8	914.5	868.3	802.2	737.5
50°	1398.3	1274.0	1213.2	1137.9	1034.8	954.2	886.8	844.5	808.8	744.1	685.9
52.5°	1264.8	1170.9	1112.8	1048.0	948.9	867.0	814.1	777.1	734.8	684.6	633.0
55°	1147.2	1059.9	1013.7	952.9	855.1	782.4	737.5	703.1	670.1	625.1	584.1
57.5°	1013.7	959.5	913.2	860.4	763.9	701.8	662.1	633.0	602.7	565.6	532.6
60°	873.6	848.5	803.5	761.2	679.3	625.1	592.1	565.6	536.6	506.2	478.4
62.5°	749.3	734.8	708.4	675.3	598.7	552.4	519.4	499.6	478.4	450.7	424.2
65°	631.7	625.1	600.0	576.2	523.4	482.4	453.3	441.4	417.6	396.5	372.7
67.5°	527.3	519.4	504.9	494.3	449.3	411.0	396.5	380.6	360.8	344.9	325.1
70°	421.6	420.3	411.0	397.8	374.0	346.3	331.7	321.1	301.3	289.4	274.9
72.5°	327.8	334.4	326.4	321.1	305.3	285.5	272.2	265.6	249.8	240.5	230.0
75°	244.5	249.8	253.7	244.5	240.5	231.3	219.4	212.8	204.8	191.6	187.7
77.5°	166.5	178.4	178.4	181.1	182.4	177.1	167.8	162.6	153.3	150.7	145.4
80°	109.7	120.3	121.6	124.2	128.2	128.2	121.6	120.3	111.0	109.7	105.7
82.5°	63.4	72.7	78.0	81.9	80.6	85.9	80.6	79.3	74.0	74.0	71.4
85°	34.4	35.7	38.3	41.0	43.6	46.3	46.3	44.9	43.6	42.3	39.6
87.5°	13.2	13.2	14.5	13.2	14.5	17.2	18.5	18.5	17.2	15.9	13.2
90°	10.3	5.9	5.9	5.9	5.1	4.4	2.2	0.7	2.2	4.4	5.1
92.5°	111.6	66.1	56.6	47.0	33.8	22.8	14.7	10.3	14.7	22.8	33.8
95°	155.7	91.8	76.4	61.0	43.3	33.8	26.4	24.2	26.4	33.8	43.3
97.5°	148.3	97.7	84.4	71.2	55.8	47.0	40.4	40.4	40.4	47.0	55.8
100°	150.6	107.2	95.4	83.7	69.8	61.0	55.8	55.8	55.8	61.0	69.8
102.5°	157.9	119.7	108.7	97.7	84.5	76.4	72.0	70.5	72.0	76.4	84.5
105°	170.4	135.1	124.4	113.8	100.6	91.8	88.1	85.9	88.1	91.8	100.6
107.5°	183.6	151.3	140.6	130.0	117.5	108.0	104.3	102.8	104.3	108.0	117.5
110°	199.0	166.7	156.8	146.9	133.7	124.8	121.2	119.7	121.2	124.8	133.7

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	213.7	182.9	173.0	163.0	149.8	141.7	137.3	135.9	137.3	141.7	149.8
115°	229.1	199.8	189.9	179.9	166.0	158.6	153.5	151.3	153.5	158.6	166.0
117.5°	243.8	215.9	205.6	195.3	182.1	174.1	169.6	167.4	169.6	174.1	182.1
120°	259.2	231.3	221.0	210.8	198.3	190.2	185.1	183.6	185.1	190.2	198.3
122.5°	273.9	246.0	236.1	226.2	212.2	204.9	199.8	198.3	199.8	204.9	212.2
125°	287.1	260.7	250.4	240.1	226.2	218.1	213.7	210.8	213.7	218.1	226.2
127.5°	299.6	273.9	263.6	253.4	238.7	229.9	224.7	222.5	224.7	229.9	238.7
130°	312.1	287.1	276.5	265.9	251.9	240.9	235.0	232.1	235.0	240.9	251.9
132.5°	322.4	297.4	287.5	277.6	262.2	251.9	243.8	241.6	243.8	251.9	262.2
135°	331.9	307.7	298.2	288.6	273.2	260.7	253.4	250.4	253.4	260.7	273.2
137.5°	339.3	316.5	307.4	298.2	282.0	270.3	262.2	259.2	262.2	270.3	282.0
140°	346.6	324.6	315.8	307.0	291.6	279.1	271.0	268.8	271.0	279.1	291.6
142.5°	353.2	331.9	323.5	315.1	300.4	288.6	281.3	279.1	281.3	288.6	300.4
145°	357.7	338.6	330.5	322.4	308.4	298.2	290.8	288.6	290.8	298.2	308.4
147.5°	362.8	344.4	337.0	329.7	318.0	307.0	300.4	299.6	300.4	307.0	318.0
150°	366.5	350.3	343.4	336.4	325.3	316.5	310.6	309.9	310.6	316.5	325.3
152.5°	369.4	355.4	349.2	343.0	333.4	325.3	319.5	319.5	319.5	325.3	333.4
155°	372.3	359.9	354.4	348.8	340.8	333.4	329.0	328.3	329.0	333.4	340.8
157.5°	374.5	363.5	359.1	354.7	347.4	341.5	337.1	337.1	337.1	341.5	347.4
160°	376.0	367.2	363.2	359.1	353.2	348.1	345.2	345.2	345.2	348.1	353.2
162.5°	377.5	369.4	366.4	363.5	358.4	354.0	351.8	352.5	351.8	354.0	358.4
165°	377.5	370.9	368.7	366.5	362.8	359.1	357.7	357.7	357.7	359.1	362.8
167.5°	377.5	372.3	370.5	368.7	366.5	363.5	362.8	363.5	362.8	363.5	366.5
170°	376.7	373.1	372.0	370.9	369.4	367.2	366.5	367.2	366.5	367.2	369.4
172.5°	376.0	373.8	373.0	372.3	371.6	370.1	370.1	370.9	370.1	370.1	371.6
175°	375.3	373.8	373.8	373.8	373.1	372.3	372.3	373.1	372.3	372.3	373.1
177.5°	374.5	373.8	373.8	373.8	373.8	373.1	373.8	374.5	373.8	373.1	373.8
180°	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1
2.5°	1613.7	1611.0	1608.4	1597.8	1588.6	1572.7	1559.5	1554.2	1552.9	1554.2	1550.2
5°	1567.4	1566.1	1556.8	1538.3	1521.2	1502.7	1489.4	1476.2	1468.3	1468.3	1459.0
7.5°	1523.8	1514.6	1506.6	1482.8	1463.0	1437.9	1418.1	1406.2	1399.6	1385.0	1385.0
10°	1477.6	1464.3	1453.8	1431.3	1402.2	1377.1	1352.0	1337.5	1325.6	1315.0	1311.0
12.5°	1431.3	1420.7	1400.9	1377.1	1348.0	1316.3	1289.9	1279.3	1251.6	1229.1	1230.4
15°	1387.7	1363.9	1354.6	1320.3	1285.9	1255.5	1217.2	1186.8	1164.3	1149.8	1131.3
17.5°	1338.8	1315.0	1297.8	1268.7	1223.8	1176.2	1139.2	1098.3	1075.8	1050.7	1038.8
20°	1284.6	1264.8	1251.6	1205.3	1151.1	1094.3	1053.3	1028.2	1003.1	984.6	974.0
22.5°	1238.3	1213.2	1197.4	1135.3	1075.8	1019.0	987.2	966.1	944.9	929.1	923.8
25°	1178.9	1164.3	1126.0	1071.8	999.1	960.8	933.1	905.3	893.4	882.8	870.9
27.5°	1130.0	1094.3	1067.9	996.5	951.6	907.9	880.2	859.0	844.5	833.9	824.7
30°	1069.2	1036.1	999.1	939.7	898.7	857.7	832.6	815.4	799.6	793.0	785.0
32.5°	1005.7	975.3	939.7	892.1	841.9	810.1	790.3	771.8	761.2	754.6	745.4
35°	948.9	910.6	886.8	841.9	800.9	765.2	746.7	730.8	719.0	716.3	715.0
37.5°	888.1	859.0	836.6	790.3	756.0	725.6	708.4	691.2	684.6	683.3	678.0
40°	835.3	810.1	789.0	745.4	708.4	680.6	667.4	656.8	650.2	650.2	648.9
42.5°	789.0	762.6	741.4	701.8	668.7	643.6	629.1	618.5	615.9	617.2	615.9
45°	737.5	715.0	693.8	652.9	625.1	606.6	590.8	585.5	581.5	582.8	584.1
47.5°	688.6	670.1	648.9	615.9	584.1	564.3	555.1	549.8	549.8	549.8	552.4
50°	644.9	623.8	605.3	570.9	541.9	526.0	518.1	511.5	512.8	514.1	515.4
52.5°	593.4	574.9	561.7	527.3	506.2	486.3	477.1	478.4	477.1	477.1	479.7
55°	548.5	530.0	516.7	485.0	463.9	450.7	442.7	438.8	440.1	437.5	442.7
57.5°	498.2	482.4	473.1	442.7	424.2	412.3	405.7	399.1	401.8	400.4	399.1
60°	454.6	436.1	421.6	400.4	384.6	370.0	366.1	359.5	362.1	359.5	358.2
62.5°	404.4	389.9	379.3	358.2	344.9	333.0	323.8	319.8	318.5	314.5	310.6
65°	354.2	346.3	335.7	314.5	301.3	292.1	286.8	282.8	281.5	270.9	259.0
67.5°	307.9	302.6	292.1	276.2	264.3	255.1	247.1	240.5	232.6	224.7	218.1
70°	264.3	256.4	249.8	235.2	224.7	215.4	207.5	199.6	195.6	187.7	185.0
72.5°	222.0	214.1	207.5	194.3	185.0	175.8	173.1	163.9	159.9	158.6	158.6
75°	178.4	171.8	167.8	155.9	148.0	141.4	137.4	134.8	132.2	129.5	125.6
77.5°	136.1	132.2	129.5	121.6	115.0	111.0	109.7	100.4	97.8	95.2	92.5
80°	99.1	97.8	95.2	88.5	85.9	76.7	76.7	74.0	72.7	72.7	72.7
82.5°	67.4	64.8	63.4	56.8	55.5	54.2	52.9	51.5	52.9	51.5	52.9
85°	35.7	34.4	33.0	33.0	33.0	33.0	33.0	33.0	33.0	31.7	33.0
87.5°	13.2	13.2	13.2	13.2	11.9	13.2	13.2	11.9	13.2	13.2	13.2
90°	5.9	5.9	5.9	10.3	10.3	11.8	13.2	12.5	13.2	14.0	14.7
92.5°	47.0	56.6	66.1	111.6	182.9	251.9	287.9	239.4	177.0	132.2	104.3
95°	61.0	76.4	91.8	155.7	276.1	451.7	598.5	615.4	544.2	430.4	331.9
97.5°	71.2	84.4	97.7	148.3	251.9	432.6	640.4	771.8	783.6	727.1	646.3
100°	83.7	95.4	107.2	150.6	233.5	383.4	590.5	778.5	885.7	900.4	864.4
102.5°	97.7	108.7	119.7	157.9	228.4	350.3	528.0	723.4	880.5	967.9	990.0
105°	113.8	124.4	135.1	170.4	231.3	334.1	481.8	654.3	822.5	949.6	1022.3
107.5°	130.0	140.6	151.3	183.6	240.1	329.7	451.7	597.8	751.3	888.6	990.0
110°	146.9	156.8	166.7	199.0	250.4	331.2	437.7	557.4	688.1	815.2	921.7

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	163.0	173.0	182.9	213.7	261.4	335.6	431.1	534.6	641.9	750.6	849.7
115°	179.9	189.9	199.8	229.1	273.2	341.5	429.6	522.2	614.0	704.3	790.2
117.5°	195.3	205.6	215.9	243.8	284.9	347.4	428.9	515.5	597.8	674.2	743.9
120°	210.8	221.0	231.3	259.2	297.4	354.0	428.9	510.4	587.5	655.8	714.6
122.5°	226.2	236.1	246.0	273.9	309.2	360.6	428.2	504.5	578.7	644.1	696.2
125°	240.1	250.4	260.7	287.1	320.9	367.2	427.4	497.9	568.4	631.6	682.3
127.5°	253.4	263.6	273.9	299.6	331.2	372.3	425.9	489.1	556.7	617.6	668.3
130°	265.9	276.5	287.1	312.1	340.8	378.2	425.2	481.0	542.0	600.0	649.9
132.5°	277.6	287.5	297.4	322.4	350.3	383.4	424.5	473.7	526.6	580.2	628.6
135°	288.6	298.2	307.7	331.9	358.4	388.5	423.7	466.3	512.6	560.3	605.1
137.5°	298.2	307.4	316.5	339.3	364.3	391.4	423.7	459.7	499.4	541.2	580.2
140°	307.0	315.8	324.6	346.6	370.1	395.1	423.0	454.6	488.4	522.9	555.9
142.5°	315.1	323.5	331.9	353.2	374.5	398.0	423.0	450.2	478.1	507.5	534.6
145°	322.4	330.5	338.6	357.7	377.5	398.8	421.5	445.0	468.5	493.5	515.5
147.5°	329.7	337.0	344.4	362.8	380.4	399.5	419.3	440.6	460.5	481.0	499.4
150°	336.4	343.4	350.3	366.5	382.6	399.5	417.1	435.5	453.1	470.0	484.7
152.5°	343.0	349.2	355.4	369.4	384.1	398.0	413.5	429.6	445.0	459.0	472.2
155°	348.8	354.4	359.9	372.3	384.8	396.6	409.8	423.7	437.0	448.7	459.7
157.5°	354.7	359.1	363.5	374.5	384.8	395.1	406.1	417.9	428.2	438.4	448.0
160°	359.1	363.2	367.2	376.0	384.8	392.9	401.7	411.3	420.1	428.2	436.2
162.5°	363.5	366.4	369.4	377.5	384.8	390.7	397.3	405.4	412.0	418.6	424.5
165°	366.5	368.7	370.9	377.5	383.4	387.8	392.9	398.8	404.7	409.1	414.2
167.5°	368.7	370.5	372.3	377.5	381.9	384.8	388.5	392.9	397.3	401.0	405.4
170°	370.9	372.0	373.1	376.7	380.4	381.9	384.1	387.0	390.7	392.9	395.8
172.5°	372.3	373.0	373.8	376.0	378.9	378.9	379.7	381.9	384.8	386.3	387.8
175°	373.8	373.8	373.8	375.3	377.5	376.7	376.7	378.2	379.7	380.4	381.9
177.5°	373.8	373.8	373.8	374.5	376.0	374.5	374.5	375.3	376.0	376.7	376.7
180°	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1
2.5°	1550.2	1555.5	1548.9	1552.9	1543.6	1542.3	1543.6	1543.6	1545.0	1546.3	1547.6
5°	1463.0	1461.7	1453.8	1448.5	1444.5	1448.5	1451.1	1453.8	1451.1	1453.8	1455.1
7.5°	1381.1	1377.1	1373.1	1363.9	1366.5	1363.9	1371.8	1367.9	1367.9	1374.5	1379.8
10°	1308.4	1300.5	1297.8	1287.2	1279.3	1278.0	1287.2	1291.2	1295.2	1297.8	1308.4
12.5°	1214.6	1202.7	1193.4	1197.4	1174.9	1184.2	1186.8	1181.5	1197.4	1215.9	1205.3
15°	1114.1	1115.4	1096.9	1090.3	1071.8	1077.1	1078.4	1091.6	1104.9	1103.5	1119.4
17.5°	1040.1	1032.2	1016.3	1015.0	1007.1	1011.0	1009.7	1020.3	1016.3	1022.9	1036.1
20°	971.4	966.1	952.9	947.6	950.2	947.6	948.9	950.2	954.2	968.7	966.1
22.5°	917.2	910.6	910.6	904.0	896.0	893.4	900.0	904.0	909.3	911.9	918.5
25°	869.6	864.3	857.7	853.8	847.1	848.5	852.4	857.7	861.7	867.0	872.3
27.5°	820.7	820.7	814.1	812.8	810.1	808.8	814.1	816.7	816.7	820.7	826.0
30°	782.4	782.4	775.8	774.5	773.1	773.1	777.1	778.4	779.7	783.7	786.4
32.5°	745.4	744.1	741.4	742.7	741.4	742.7	742.7	744.1	746.7	748.0	753.3
35°	711.0	712.3	709.7	709.7	708.4	709.7	712.3	713.7	715.0	717.6	717.6
37.5°	678.0	680.6	679.3	683.3	683.3	683.3	683.3	685.9	685.9	685.9	684.6
40°	648.9	648.9	647.6	650.2	652.9	652.9	654.2	654.2	655.5	655.5	654.2
42.5°	615.9	618.5	622.5	623.8	626.4	625.1	629.1	627.8	629.1	626.4	623.8
45°	585.5	585.5	590.8	596.0	597.4	597.4	597.4	600.0	597.4	593.4	592.1
47.5°	552.4	555.1	557.7	564.3	565.6	565.6	565.6	565.6	563.0	563.0	563.0
50°	519.4	520.7	522.0	524.7	528.6	527.3	527.3	527.3	532.6	527.3	528.6
52.5°	479.7	481.1	482.4	487.7	486.3	486.3	487.7	487.7	491.6	490.3	487.7
55°	440.1	440.1	442.7	442.7	442.7	445.4	446.7	449.3	448.0	449.3	450.7
57.5°	400.4	397.8	396.5	396.5	400.4	399.1	400.4	400.4	405.7	408.4	409.7
60°	354.2	354.2	352.9	344.9	344.9	343.6	347.6	350.2	352.9	364.8	363.4
62.5°	306.6	301.3	296.0	297.4	289.4	293.4	290.8	293.4	301.3	310.6	311.9
65°	259.0	255.1	249.8	248.5	245.8	249.8	248.5	249.8	253.7	259.0	265.6
67.5°	216.7	215.4	212.8	211.5	211.5	211.5	214.1	214.1	215.4	219.4	223.4
70°	185.0	183.7	185.0	182.4	183.7	182.4	183.7	185.0	186.3	187.7	191.6
72.5°	155.9	155.9	155.9	153.3	155.9	154.6	154.6	155.9	157.3	158.6	161.2
75°	124.2	121.6	118.9	116.3	115.0	117.6	118.9	117.6	121.6	126.9	126.9
77.5°	93.8	92.5	92.5	92.5	93.8	92.5	95.2	93.8	95.2	95.2	97.8
80°	72.7	71.4	72.7	72.7	71.4	74.0	72.7	72.7	74.0	75.3	74.0
82.5°	52.9	54.2	52.9	52.9	52.9	55.5	52.9	52.9	52.9	54.2	54.2
85°	33.0	33.0	33.0	33.0	34.4	33.0	34.4	33.0	35.7	34.4	34.4
87.5°	11.9	13.2	14.5	14.5	14.5	14.5	13.2	14.5	15.9	14.5	15.9
90°	14.7	14.7	15.4	16.2	15.4	15.4	15.4	16.2	15.4	14.7	14.7
92.5°	95.1	85.9	74.9	69.8	66.8	66.8	66.8	69.8	74.9	85.9	95.1
95°	296.3	260.7	224.7	202.0	188.7	179.2	188.7	202.0	224.7	260.7	296.3
97.5°	605.2	564.0	514.1	470.0	448.0	430.4	448.0	470.0	514.1	564.0	605.2
100°	837.2	810.0	746.1	701.3	679.3	673.4	679.3	701.3	746.1	810.0	837.2
102.5°	982.6	975.3	942.2	912.9	889.4	884.9	889.4	912.9	942.2	975.3	982.6
105°	1037.4	1052.4	1053.9	1048.0	1037.7	1033.3	1037.7	1048.0	1053.9	1052.4	1037.4
107.5°	1020.8	1051.7	1084.0	1097.2	1103.1	1103.8	1103.1	1097.2	1084.0	1051.7	1020.8
110°	962.0	1002.4	1054.6	1085.4	1098.7	1105.3	1098.7	1085.4	1054.6	1002.4	962.0

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	890.1	930.5	991.4	1030.4	1050.2	1061.9	1050.2	1030.4	991.4	930.5	890.1
115°	825.4	860.7	918.7	962.8	986.3	992.2	986.3	962.8	918.7	860.7	825.4
117.5°	774.8	805.6	857.0	895.2	920.2	923.9	920.2	895.2	857.0	805.6	774.8
120°	740.7	766.7	808.6	840.9	860.0	868.1	860.0	840.9	808.6	766.7	740.7
122.5°	718.2	740.3	774.1	800.5	815.9	824.0	815.9	800.5	774.1	740.3	718.2
125°	702.4	722.6	752.0	773.3	787.3	791.7	787.3	773.3	752.0	722.6	702.4
127.5°	687.4	706.5	735.9	755.0	766.7	771.1	766.7	755.0	735.9	706.5	687.4
130°	669.4	688.9	719.0	737.3	749.1	753.5	749.1	737.3	719.0	688.9	669.4
132.5°	648.1	667.6	696.9	718.2	729.3	733.7	729.3	718.2	696.9	667.6	648.1
135°	623.5	641.9	671.2	691.8	703.5	708.0	703.5	691.8	671.2	641.9	623.5
137.5°	597.1	614.0	641.9	663.2	672.7	677.8	672.7	663.2	641.9	614.0	597.1
140°	571.3	586.8	612.5	628.6	638.9	644.8	638.9	628.6	612.5	586.8	571.3
142.5°	547.4	560.3	582.4	597.1	605.9	609.5	605.9	597.1	582.4	560.3	547.4
145°	525.8	536.1	554.5	567.0	574.3	578.0	574.3	567.0	554.5	536.1	525.8
147.5°	507.8	516.3	530.2	541.2	547.1	548.6	547.1	541.2	530.2	516.3	507.8
150°	491.3	497.9	509.7	519.2	523.6	524.4	523.6	519.2	509.7	497.9	491.3
152.5°	477.4	482.5	492.0	499.4	501.6	502.3	501.6	499.4	492.0	482.5	477.4
155°	464.1	468.5	475.9	481.8	484.0	484.0	484.0	481.8	475.9	468.5	464.1
157.5°	451.6	455.3	461.2	465.6	467.1	467.1	467.1	465.6	461.2	455.3	451.6
160°	439.2	442.1	446.5	450.9	451.7	451.7	451.7	450.9	446.5	442.1	439.2
162.5°	427.0	429.6	432.6	437.0	437.7	437.0	437.7	437.0	432.6	429.6	427.0
165°	416.0	417.9	420.8	423.7	423.0	422.3	423.0	423.7	420.8	417.9	416.0
167.5°	406.5	407.6	409.1	411.3	411.3	410.5	411.3	411.3	409.1	407.6	406.5
170°	396.9	398.0	399.5	400.2	399.5	399.5	399.5	400.2	399.5	398.0	396.9
172.5°	388.5	389.2	390.0	390.7	390.0	388.5	390.0	390.7	390.0	389.2	388.5
175°	381.9	381.9	381.9	383.4	381.9	380.4	381.9	383.4	381.9	381.9	381.9
177.5°	377.1	377.5	376.7	377.5	376.0	374.5	376.0	377.5	376.7	377.5	377.1
180°	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1	1640.1
2.5°	1552.9	1559.5	1556.8	1547.6	1551.6	1559.5	1567.4	1578.0	1584.6	1589.9	1592.5
5°	1461.7	1473.6	1470.9	1470.9	1476.2	1489.4	1502.7	1525.1	1533.1	1542.3	1555.5
7.5°	1381.1	1390.3	1398.3	1400.9	1408.8	1426.0	1443.2	1468.3	1488.1	1498.7	1506.6
10°	1309.7	1316.3	1328.2	1334.8	1342.7	1363.9	1389.0	1415.4	1435.3	1453.8	1464.3
12.5°	1218.5	1244.9	1260.8	1271.4	1282.0	1313.7	1333.5	1362.6	1386.4	1403.5	1419.4
15°	1116.8	1148.5	1157.7	1198.7	1225.1	1250.2	1280.6	1315.0	1337.5	1357.3	1378.4
17.5°	1030.8	1053.3	1063.9	1107.5	1130.0	1169.6	1213.2	1256.8	1291.2	1305.7	1326.9
20°	976.7	988.6	1009.7	1024.2	1048.0	1094.3	1141.9	1194.7	1246.3	1260.8	1282.0
22.5°	921.2	937.0	951.6	971.4	989.9	1021.6	1069.2	1127.3	1182.8	1209.3	1234.4
25°	870.9	886.8	896.0	917.2	934.4	966.1	999.1	1058.6	1124.7	1147.2	1186.8
27.5°	831.3	840.5	856.4	865.6	885.5	914.5	944.9	989.9	1054.6	1093.0	1131.3
30°	791.6	798.2	811.5	824.7	839.2	859.0	893.4	937.0	996.5	1029.5	1067.9
32.5°	752.0	762.6	770.5	779.7	795.6	819.4	843.2	885.5	933.1	970.1	1008.4
35°	719.0	722.9	733.5	744.1	754.6	775.8	800.9	841.9	884.2	913.2	947.6
37.5°	683.3	689.9	697.8	701.8	719.0	732.2	758.6	790.3	840.5	859.0	893.4
40°	655.5	654.2	662.1	668.7	676.7	697.8	713.7	748.0	787.7	816.7	837.9
42.5°	621.2	621.2	623.8	631.7	642.3	655.5	674.0	703.1	744.1	765.2	790.3
45°	593.4	589.4	590.8	596.0	602.7	615.9	634.4	659.5	700.4	717.6	744.1
47.5°	560.4	556.4	556.4	561.7	567.0	576.2	590.8	619.8	652.9	675.3	695.2
50°	523.4	524.7	523.4	527.3	530.0	539.2	555.1	578.9	609.3	627.8	650.2
52.5°	489.0	486.3	485.0	487.7	493.0	499.6	516.7	537.9	567.0	585.5	605.3
55°	446.7	449.3	449.3	449.3	457.3	459.9	473.1	494.3	523.4	537.9	556.4
57.5°	408.4	407.1	409.7	408.4	415.0	424.2	434.8	450.7	479.7	494.3	511.5
60°	366.1	367.4	368.7	368.7	374.0	383.3	395.2	409.7	433.5	448.0	463.9
62.5°	314.5	321.1	327.8	330.4	338.3	344.9	352.9	368.7	389.9	400.4	415.0
65°	265.6	274.9	284.1	290.8	296.0	302.6	313.2	327.8	344.9	355.5	370.0
67.5°	223.4	230.0	241.9	248.5	259.0	267.0	273.6	285.5	306.6	310.6	322.5
70°	193.0	195.6	200.9	206.2	218.1	224.7	232.6	244.5	260.4	269.6	276.2
72.5°	162.6	163.9	166.5	171.8	177.1	185.0	194.3	204.8	219.4	223.4	232.6
75°	129.5	137.4	137.4	141.4	145.4	149.3	157.3	167.8	177.1	183.7	189.0
77.5°	96.5	100.4	103.1	109.7	115.0	118.9	124.2	132.2	137.4	142.7	146.7
80°	75.3	76.7	78.0	78.0	80.6	85.9	91.2	96.5	103.1	105.7	109.7
82.5°	55.5	55.5	55.5	58.2	59.5	60.8	60.8	63.4	70.0	72.7	76.7
85°	35.7	35.7	35.7	35.7	37.0	38.3	39.6	41.0	41.0	41.0	43.6
87.5°	14.5	17.2	15.9	17.2	17.2	17.2	17.2	18.5	18.5	19.8	19.8
90°	14.7	14.0	13.2	12.5	13.2	11.8	10.3	10.3	5.9	5.9	5.9
92.5°	104.3	132.2	177.0	239.4	287.9	251.9	182.9	111.6	66.1	56.6	47.0
95°	331.9	430.4	544.2	615.4	598.5	451.7	276.1	155.7	91.8	76.4	61.0
97.5°	646.3	727.1	783.6	771.8	640.4	432.6	251.9	148.3	97.7	84.4	71.2
100°	864.4	900.4	885.7	778.5	590.5	383.4	233.5	150.6	107.2	95.4	83.7
102.5°	990.0	967.9	880.5	723.4	528.0	350.3	228.4	157.9	119.7	108.7	97.7
105°	1022.3	949.6	822.5	654.3	481.8	334.1	231.3	170.4	135.1	124.4	113.8
107.5°	990.0	888.6	751.3	597.8	451.7	329.7	240.1	183.6	151.3	140.6	130.0
110°	921.7	815.2	688.1	557.4	437.7	331.2	250.4	199.0	166.7	156.8	146.9

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	849.7	750.6	641.9	534.6	431.1	335.6	261.4	213.7	182.9	173.0	163.0
115°	790.2	704.3	614.0	522.2	429.6	341.5	273.2	229.1	199.8	189.9	179.9
117.5°	743.9	674.2	597.8	515.5	428.9	347.4	284.9	243.8	215.9	205.6	195.3
120°	714.6	655.8	587.5	510.4	428.9	354.0	297.4	259.2	231.3	221.0	210.8
122.5°	696.2	644.1	578.7	504.5	428.2	360.6	309.2	273.9	246.0	236.1	226.2
125°	682.3	631.6	568.4	497.9	427.4	367.2	320.9	287.1	260.7	250.4	240.1
127.5°	668.3	617.6	556.7	489.1	425.9	372.3	331.2	299.6	273.9	263.6	253.4
130°	649.9	600.0	542.0	481.0	425.2	378.2	340.8	312.1	287.1	276.5	265.9
132.5°	628.6	580.2	526.6	473.7	424.5	383.4	350.3	322.4	297.4	287.5	277.6
135°	605.1	560.3	512.6	466.3	423.7	388.5	358.4	331.9	307.7	298.2	288.6
137.5°	580.2	541.2	499.4	459.7	423.7	391.4	364.3	339.3	316.5	307.4	298.2
140°	555.9	522.9	488.4	454.6	423.0	395.1	370.1	346.6	324.6	315.8	307.0
142.5°	534.6	507.5	478.1	450.2	423.0	398.0	374.5	353.2	331.9	323.5	315.1
145°	515.5	493.5	468.5	445.0	421.5	398.8	377.5	357.7	338.6	330.5	322.4
147.5°	499.4	481.0	460.5	440.6	419.3	399.5	380.4	362.8	344.4	337.0	329.7
150°	484.7	470.0	453.1	435.5	417.1	399.5	382.6	366.5	350.3	343.4	336.4
152.5°	472.2	459.0	445.0	429.6	413.5	398.0	384.1	369.4	355.4	349.2	343.0
155°	459.7	448.7	437.0	423.7	409.8	396.6	384.8	372.3	359.9	354.4	348.8
157.5°	448.0	438.4	428.2	417.9	406.1	395.1	384.8	374.5	363.5	359.1	354.7
160°	436.2	428.2	420.1	411.3	401.7	392.9	384.8	376.0	367.2	363.2	359.1
162.5°	424.5	418.6	412.0	405.4	397.3	390.7	384.8	377.5	369.4	366.4	363.5
165°	414.2	409.1	404.7	398.8	392.9	387.8	383.4	377.5	370.9	368.7	366.5
167.5°	405.4	401.0	397.3	392.9	388.5	384.8	381.9	377.5	372.3	370.5	368.7
170°	395.8	392.9	390.7	387.0	384.1	381.9	380.4	376.7	373.1	372.0	370.9
172.5°	387.8	386.3	384.8	381.9	379.7	378.9	378.9	376.0	373.8	373.0	372.3
175°	381.9	380.4	379.7	378.2	376.7	376.7	377.5	375.3	373.8	373.8	373.8
177.5°	376.7	376.7	376.0	375.3	374.5	374.5	376.0	374.5	373.8	373.8	373.8
180°	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8	373.8

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1640.1	1640.1	1640.1	1640.1
2.5°	1603.1	1611.0	1624.2	1642.8
5°	1566.1	1588.6	1609.7	1637.5
7.5°	1533.1	1559.5	1588.6	1628.2
10°	1494.7	1527.8	1564.8	1613.7
12.5°	1449.8	1496.1	1538.3	1591.2
15°	1416.8	1451.1	1505.3	1567.4
17.5°	1370.5	1416.8	1470.9	1541.0
20°	1326.9	1375.8	1436.6	1509.3
22.5°	1280.6	1336.1	1396.9	1474.9
25°	1233.1	1292.5	1353.3	1436.6
27.5°	1189.4	1243.6	1312.4	1396.9
30°	1136.6	1198.7	1264.8	1353.3
32.5°	1085.0	1149.8	1217.2	1305.7
35°	1029.5	1094.3	1168.3	1252.9
37.5°	975.3	1046.7	1114.1	1196.0
40°	915.9	989.9	1059.9	1143.2
42.5°	857.7	934.4	1004.4	1075.8
45°	803.5	878.9	942.3	1009.7
47.5°	752.0	819.4	884.2	944.9
50°	701.8	758.6	818.1	868.3
52.5°	648.9	703.1	750.7	795.6
55°	601.3	643.6	685.9	726.9
57.5°	544.5	586.8	623.8	655.5
60°	496.9	523.4	559.0	592.1
62.5°	442.7	473.1	500.9	522.0
65°	389.9	416.3	437.5	456.0
67.5°	344.9	360.8	376.7	396.5
70°	290.8	304.0	322.5	337.0
72.5°	244.5	255.1	264.3	281.5
75°	198.2	207.5	212.8	228.6
77.5°	153.3	162.6	166.5	175.8
80°	117.6	118.9	124.2	132.2
82.5°	80.6	83.3	84.6	91.2
85°	46.3	52.9	51.5	54.2
87.5°	19.8	21.1	23.8	26.4
90°	5.1	4.4	2.2	0.7
92.5°	33.8	22.8	14.7	10.3
95°	43.3	33.8	26.4	24.2
97.5°	55.8	47.0	40.4	40.4
100°	69.8	61.0	55.8	55.8
102.5°	84.5	76.4	72.0	70.5
105°	100.6	91.8	88.1	85.9
107.5°	117.5	108.0	104.3	102.8
110°	133.7	124.8	121.2	119.7

TEST NUMBER: P1026075

CATALOG NUMBER: S124RDIP-B1020D810UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	149.8	141.7	137.3	135.9
115°	166.0	158.6	153.5	151.3
117.5°	182.1	174.1	169.6	167.4
120°	198.3	190.2	185.1	183.6
122.5°	212.2	204.9	199.8	198.3
125°	226.2	218.1	213.7	210.8
127.5°	238.7	229.9	224.7	222.5
130°	251.9	240.9	235.0	232.1
132.5°	262.2	251.9	243.8	241.6
135°	273.2	260.7	253.4	250.4
137.5°	282.0	270.3	262.2	259.2
140°	291.6	279.1	271.0	268.8
142.5°	300.4	288.6	281.3	279.1
145°	308.4	298.2	290.8	288.6
147.5°	318.0	307.0	300.4	299.6
150°	325.3	316.5	310.6	309.9
152.5°	333.4	325.3	319.5	319.5
155°	340.8	333.4	329.0	328.3
157.5°	347.4	341.5	337.1	337.1
160°	353.2	348.1	345.2	345.2
162.5°	358.4	354.0	351.8	352.5
165°	362.8	359.1	357.7	357.7
167.5°	366.5	363.5	362.8	363.5
170°	369.4	367.2	366.5	367.2
172.5°	371.6	370.1	370.1	370.9
175°	373.1	372.3	372.3	373.1
177.5°	373.8	373.1	373.8	374.5
180°	373.8	373.8	373.8	373.8

(END OF REPORT)