

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026153

Luminaire Tested: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026153
REPORT IS A COMBINATION OF REPORTS P999123 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6367.0 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	79			
1	105	101	97	94	100	97	93	90	89	86	84	81	79	77	75	73	72	68			
2	96	89	83	78	92	85	80	75	79	74	70	72	69	66	67	64	61	58			
3	88	79	72	66	84	76	69	64	70	65	60	65	60	57	60	56	53	50			
4	81	70	62	56	77	68	60	55	63	57	52	58	53	49	54	50	46	44			
5	75	63	55	49	71	61	53	48	57	50	45	52	47	43	49	44	41	38			
6	69	57	49	43	66	55	48	42	51	45	40	48	42	38	44	40	36	34			
7	64	52	44	38	61	50	43	37	47	40	36	44	38	34	41	36	32	30			
8	60	47	40	34	57	46	38	33	43	37	32	40	35	31	37	33	29	27			
9	56	44	36	31	54	42	35	30	40	33	29	37	32	28	35	30	27	25			
10	53	40	33	28	50	39	32	27	37	30	26	34	29	25	32	28	24	22			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16265	16265	16265	16265
5°	16264	18378	16291	14047
10°	16178	21186	16165	12216
15°	15985	23844	15985	10228
20°	15784	25851	15701	9007
25°	15537	25962	15466	8134
30°	15276	22077	15157	7535
35°	14906	16657	14718	7088
40°	14495	12072	14210	6739
45°	13815	9175	13472	6430
50°	13008	7415	12652	5977
55°	12134	6140	11736	5374
60°	11255	5192	10753	4470
65°	10155	4229	9831	3553
70°	9143	3429	8714	2886
75°	8011	2472	7458	2114
80°	6609	1638	6017	1555
85°	4795	843	3973	843

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 20362 cd/sqm

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.1	3.0
10°-20°	583.2	9.2
20°-30°	913.6	14.3
30°-40°	1014.5	15.9
40°-50°	899.0	14.1
50°-60°	700.6	11.0
60°-70°	458.3	7.2
70°-80°	224.9	3.5
80°-90°	55.5	0.9
90°-100°	131.8	2.1
100°-110°	275.1	4.3
110°-120°	244.6	3.8
120°-130°	205.9	3.2
130°-140°	171.8	2.7
140°-150°	131.1	2.1
150°-160°	92.2	1.4
160°-170°	54.2	0.9
170°-180°	17.6	0.3
0°-30°	1690.0	26.5
0°-40°	2704.5	42.5
0°-60°	4304.1	67.6
0°-90°	5042.7	79.2
90°-120°	651.5	10.2
90°-150°	1160.2	18.2
90°-180°	1324.0	20.8
0°-180°	6367.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1995	1995	1995	1995	1995	
5°	1991	2305	1995	1762	1991	189
15°	1906	3054	1906	1310	1906	538
25°	1747	3293	1739	1032	1747	805
35°	1524	2028	1504	863	1524	952
45°	1228	1037	1197	726	1228	947
55°	884	619	855	542	884	790
65°	554	362	537	304	554	553
75°	278	167	259	143	278	295
85°	66	40	55	40	66	74
90°	0	8	0	8	0	5
95°	12	87	12	87	12	13
105°	42	503	42	503	42	45
115°	74	483	74	483	74	73
125°	102	385	102	385	102	91
135°	122	344	122	344	122	94
145°	140	281	140	281	140	88
155°	160	235	160	235	160	74
165°	174	205	174	205	174	49
175°	182	185	182	185	182	17
180°	182	182	182	182	182	

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6
2.5°	1997.8	2015.4	2025.1	2033.1	2049.2	2055.6	2068.5	2071.7	2084.6	2083.0	2078.1
5°	1991.3	2021.9	2044.4	2068.5	2097.4	2113.5	2131.2	2156.9	2169.7	2187.4	2198.7
7.5°	1980.1	2021.9	2058.8	2095.8	2142.4	2168.1	2190.6	2230.8	2264.6	2293.5	2325.6
10°	1962.4	2015.4	2070.1	2119.9	2184.2	2214.7	2248.5	2308.0	2354.6	2394.8	2446.2
12.5°	1935.1	2009.0	2070.1	2137.6	2219.6	2261.4	2306.4	2377.1	2431.7	2497.6	2561.9
15°	1906.2	1988.1	2068.5	2156.9	2250.1	2298.3	2343.3	2438.1	2521.7	2597.3	2668.0
17.5°	1874.0	1964.0	2052.4	2150.5	2263.0	2322.4	2375.5	2489.6	2581.2	2679.2	2749.9
20°	1835.4	1933.5	2034.7	2144.0	2271.0	2336.9	2396.4	2526.5	2627.8	2733.9	2822.3
22.5°	1793.7	1899.7	2010.6	2129.6	2261.4	2333.7	2402.8	2542.6	2659.9	2758.0	2876.9
25°	1747.0	1859.5	1973.7	2099.0	2246.9	2325.6	2396.4	2534.6	2659.9	2788.5	2904.2
27.5°	1698.8	1814.5	1933.5	2065.3	2216.4	2293.5	2373.9	2507.3	2653.5	2793.3	2910.7
30°	1645.8	1758.3	1883.7	2009.0	2169.7	2246.9	2328.9	2473.5	2632.6	2772.4	2899.4
32.5°	1587.9	1703.6	1822.6	1952.8	2110.3	2193.8	2269.4	2433.3	2595.7	2733.9	2852.8
35°	1523.6	1632.9	1745.4	1878.8	2034.7	2110.3	2200.3	2370.6	2534.6	2680.8	2758.0
37.5°	1454.5	1559.0	1663.5	1795.3	1944.7	2036.3	2124.7	2296.7	2470.3	2568.3	2608.5
40°	1390.2	1481.9	1573.5	1700.4	1851.5	1946.3	2036.3	2214.7	2367.4	2443.0	2412.4
42.5°	1308.3	1403.1	1485.1	1602.4	1755.1	1843.5	1935.1	2119.9	2243.7	2274.2	2198.7
45°	1227.9	1306.7	1385.4	1499.5	1660.3	1735.8	1833.8	2005.8	2108.7	2081.3	1970.4
47.5°	1149.2	1213.4	1287.4	1398.3	1542.9	1632.9	1724.5	1874.0	1946.3	1907.8	1753.5
50°	1055.9	1120.2	1197.4	1293.8	1433.6	1520.4	1592.8	1731.0	1785.6	1690.8	1504.4
52.5°	967.5	1023.8	1089.7	1179.7	1313.1	1391.8	1470.6	1589.5	1607.2	1497.9	1301.8
55°	884.0	929.0	998.1	1070.4	1192.6	1276.1	1330.8	1432.0	1427.2	1290.6	1121.8
57.5°	797.2	839.0	885.6	961.1	1076.8	1139.5	1199.0	1287.4	1240.8	1125.1	957.9
60°	720.0	744.1	790.8	863.1	961.1	1015.8	1062.4	1110.6	1070.4	945.0	816.5
62.5°	634.9	662.2	695.9	753.8	840.6	892.0	925.8	946.6	904.9	808.4	691.1
65°	554.5	578.6	614.0	665.4	731.3	769.9	787.5	802.0	779.5	670.2	577.0
67.5°	482.2	498.2	530.4	564.1	634.9	644.5	668.6	675.0	630.0	546.5	472.5
70°	409.8	425.9	440.4	480.6	512.7	530.4	535.2	535.2	490.2	435.6	374.5
72.5°	342.3	352.0	366.4	393.8	411.4	424.3	430.7	422.7	380.9	335.9	290.9
75°	278.0	282.9	295.7	313.4	327.9	323.1	321.4	311.8	281.3	249.1	223.4
77.5°	213.8	217.0	231.4	236.3	236.3	241.1	234.7	225.0	199.3	175.2	163.9
80°	160.7	165.5	167.2	170.4	167.2	167.2	162.3	146.3	133.4	122.1	114.1
82.5°	110.9	114.1	115.7	110.9	114.1	109.3	101.3	90.0	82.0	80.4	77.1
85°	65.9	67.5	65.9	65.9	61.1	59.5	53.0	51.4	48.2	48.2	46.6
87.5°	32.1	30.5	27.3	24.1	24.1	22.5	24.1	20.9	24.1	22.5	20.9
90°	0.4	1.1	2.1	2.5	2.9	2.9	2.9	5.0	5.0	5.7	6.4
92.5°	5.0	7.1	11.1	16.4	22.9	27.5	32.1	54.3	88.9	122.5	140.0
95°	11.8	12.9	16.4	21.1	29.6	37.2	44.7	75.7	134.3	219.7	291.1
97.5°	19.6	19.6	22.9	27.1	34.7	41.1	47.5	72.2	122.5	210.4	311.5
100°	27.1	27.1	29.6	33.9	40.7	46.4	52.2	73.2	113.6	186.5	287.2
102.5°	34.3	35.0	37.2	41.1	47.5	52.8	58.2	76.8	111.1	170.4	256.8
105°	41.8	42.9	44.7	48.9	55.4	60.6	65.7	82.9	112.5	162.5	234.3
107.5°	50.0	50.7	52.5	57.2	63.2	68.4	73.6	89.3	116.8	160.4	219.7
110°	58.2	58.9	60.7	65.0	71.4	76.2	81.1	96.8	121.8	161.1	212.9

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	66.1	66.8	68.9	72.9	79.3	84.1	88.9	104.0	127.2	163.3	209.7
115°	73.6	74.7	77.2	80.7	87.5	92.4	97.2	111.5	132.9	166.1	209.0
117.5°	81.4	82.5	84.7	88.6	95.0	100.0	105.0	118.6	138.6	169.0	208.6
120°	89.3	90.0	92.5	96.4	102.5	107.5	112.5	126.1	144.7	172.2	208.6
122.5°	96.4	97.2	99.7	103.2	110.0	114.8	119.7	133.2	150.4	175.4	208.3
125°	102.5	104.0	106.1	110.0	116.8	121.8	126.8	139.7	156.1	178.6	207.9
127.5°	108.2	109.3	111.8	116.1	123.2	128.2	133.2	145.7	161.1	181.1	207.2
130°	112.9	114.3	117.2	122.5	129.3	134.5	139.7	151.8	165.8	184.0	206.8
132.5°	117.5	118.6	122.5	127.5	135.0	139.8	144.7	156.8	170.4	186.5	206.5
135°	121.8	123.2	126.8	132.9	140.4	145.0	149.7	161.5	174.3	189.0	206.1
137.5°	126.1	127.5	131.5	137.2	145.0	149.5	154.0	165.0	177.2	190.4	206.1
140°	130.7	131.8	135.7	141.8	149.3	153.6	157.9	168.6	180.0	192.2	205.8
142.5°	135.7	136.8	140.4	146.1	153.2	157.4	161.5	171.8	182.2	193.6	205.8
145°	140.4	141.5	145.0	150.0	156.8	160.8	164.7	174.0	183.6	194.0	205.0
147.5°	145.7	146.1	149.3	154.7	160.4	164.0	167.5	176.5	185.0	194.3	204.0
150°	150.7	151.1	154.0	158.2	163.6	167.0	170.4	178.3	186.1	194.3	202.9
152.5°	155.4	155.4	158.2	162.2	166.8	169.9	172.9	179.7	186.8	193.6	201.1
155°	159.7	160.0	162.2	165.8	169.7	172.4	175.0	181.1	187.2	192.9	199.3
157.5°	164.0	164.0	166.1	169.0	172.5	174.6	176.8	182.2	187.2	192.2	197.5
160°	167.9	167.9	169.3	171.8	174.7	176.6	178.6	182.9	187.2	191.1	195.4
162.5°	171.5	171.1	172.2	174.3	176.8	178.2	179.7	183.6	187.2	190.0	193.3
165°	174.0	174.0	174.7	176.5	178.3	179.4	180.4	183.6	186.5	188.6	191.1
167.5°	176.8	176.5	176.8	178.3	179.3	180.2	181.1	183.6	185.8	187.2	189.0
170°	178.6	178.3	178.6	179.7	180.4	181.0	181.5	183.3	185.0	185.8	186.8
172.5°	180.4	180.0	180.0	180.8	181.1	181.4	181.8	182.9	184.3	184.3	184.7
175°	181.5	181.1	181.1	181.5	181.8	181.8	181.8	182.5	183.6	183.3	183.3
177.5°	182.2	181.8	181.5	181.8	181.8	181.8	181.8	182.2	182.9	182.2	182.2
180°	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6
2.5°	2091.0	2108.7	2110.3	2126.3	2121.5	2113.5	2128.0	2118.3	2137.6	2131.2	2139.2
5°	2213.1	2237.2	2258.1	2271.0	2293.5	2288.7	2312.8	2304.7	2322.4	2304.7	2327.2
7.5°	2356.2	2396.4	2417.3	2451.0	2460.6	2462.3	2491.2	2497.6	2508.9	2497.6	2510.5
10°	2496.0	2544.2	2592.4	2619.8	2637.4	2661.5	2687.3	2698.5	2706.6	2695.3	2703.3
12.5°	2623.0	2698.5	2751.6	2806.2	2819.1	2839.9	2867.3	2864.1	2896.2	2889.8	2904.2
15°	2740.3	2823.9	2888.2	2931.6	2966.9	2984.6	3036.0	3039.2	3037.6	3053.7	3044.1
17.5°	2844.8	2915.5	3007.1	3063.4	3106.7	3106.7	3135.7	3195.1	3190.3	3188.7	3198.4
20°	2930.0	3010.3	3095.5	3190.3	3225.7	3232.1	3272.3	3302.8	3307.6	3307.6	3307.6
22.5°	2994.2	3089.1	3180.7	3248.2	3275.5	3298.0	3333.4	3352.7	3359.1	3355.9	3359.1
25°	3026.4	3116.4	3209.6	3270.7	3286.8	3299.6	3302.8	3314.1	3312.5	3293.2	3304.4
27.5°	3032.8	3119.6	3180.7	3196.8	3188.7	3180.7	3129.2	3134.1	3119.6	3090.7	3101.9
30°	3003.9	3050.5	3048.9	2999.1	2984.6	2950.8	2904.2	2835.1	2778.9	2754.8	2762.8
32.5°	2899.4	2899.4	2841.6	2729.1	2679.2	2618.2	2534.6	2471.9	2398.0	2381.9	2412.4
35°	2754.8	2672.8	2566.7	2418.9	2343.3	2298.3	2153.7	2108.7	2046.0	2028.3	2042.8
37.5°	2529.8	2393.1	2238.9	2100.6	2036.3	1956.0	1829.0	1764.7	1719.7	1689.2	1703.6
40°	2277.4	2111.9	1951.2	1780.8	1710.1	1644.2	1549.4	1491.5	1419.2	1422.4	1427.2
42.5°	2036.3	1841.9	1661.9	1504.4	1436.9	1382.2	1316.3	1245.6	1219.9	1211.8	1203.8
45°	1780.8	1573.5	1404.7	1287.4	1226.3	1174.9	1113.8	1073.6	1043.1	1036.7	1044.7
47.5°	1539.7	1364.5	1203.8	1094.5	1044.7	1019.0	970.8	933.8	914.5	898.4	908.1
50°	1321.1	1157.2	1028.6	937.0	901.6	884.0	839.0	819.7	800.4	795.6	794.0
52.5°	1141.1	1001.3	890.4	816.5	789.1	779.5	745.7	718.4	702.4	707.2	710.4
55°	977.2	858.3	771.5	712.0	689.5	678.2	654.1	634.9	623.6	618.8	622.0
57.5°	832.5	729.7	667.0	618.8	601.1	596.3	570.6	564.1	556.1	551.3	551.3
60°	700.7	628.4	570.6	543.2	524.0	519.1	499.8	491.8	490.2	485.4	482.2
62.5°	589.8	530.4	490.2	461.3	453.2	451.6	438.8	429.1	424.3	421.1	421.1
65°	493.4	450.0	416.3	395.4	388.9	385.7	371.3	368.1	364.8	361.6	360.0
67.5°	411.4	372.9	348.8	334.3	326.3	327.9	319.8	313.4	313.4	311.8	310.2
70°	332.7	308.6	287.7	279.7	276.4	273.2	270.0	265.2	263.6	263.6	263.6
72.5°	262.0	245.9	234.7	229.8	226.6	223.4	220.2	220.2	220.2	218.6	218.6
75°	200.9	194.5	186.4	181.6	181.6	184.8	180.0	175.2	170.4	167.2	168.8
77.5°	151.1	147.9	143.0	135.0	136.6	133.4	133.4	130.2	131.8	131.8	128.6
80°	110.9	106.1	104.5	99.6	101.3	99.6	98.0	98.0	94.8	94.8	94.8
82.5°	77.1	72.3	72.3	70.7	69.1	69.1	67.5	67.5	69.1	65.9	65.9
85°	46.6	45.0	45.0	41.8	41.8	41.8	41.8	43.4	41.8	40.2	40.2
87.5°	20.9	22.5	20.9	19.3	19.3	19.3	17.7	17.7	16.1	17.7	17.7
90°	6.1	6.4	6.8	7.1	7.1	7.1	7.5	7.9	7.5	7.5	7.5
92.5°	116.5	86.1	64.3	50.7	46.2	41.8	36.4	33.9	32.5	32.5	32.5
95°	299.4	264.7	209.3	161.5	144.2	126.8	109.3	98.2	91.8	87.2	91.8
97.5°	375.4	381.2	353.6	314.4	294.4	274.3	250.1	228.6	217.9	209.3	217.9
100°	378.7	430.8	438.0	420.5	407.2	394.0	362.9	341.1	330.4	327.6	330.4
102.5°	351.9	428.3	470.8	481.5	478.0	474.4	458.3	444.0	432.6	430.5	432.6
105°	318.3	400.1	461.9	497.3	504.6	511.9	512.6	509.8	504.8	502.6	504.8
107.5°	290.8	365.4	432.2	481.5	496.5	511.5	527.3	533.7	536.5	536.9	536.5
110°	271.1	334.7	396.5	448.3	468.0	487.6	513.0	528.0	534.4	537.6	534.4

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	260.1	312.2	365.1	413.3	433.0	452.6	482.2	501.2	510.8	516.5	510.8
115°	254.0	298.6	342.6	384.4	401.5	418.7	446.9	468.3	479.7	482.6	479.7
117.5°	250.8	290.8	327.9	361.9	376.9	391.9	416.9	435.5	447.6	449.4	447.6
120°	248.3	285.8	319.0	347.6	360.2	372.9	393.3	409.0	418.3	422.2	418.3
122.5°	245.4	281.5	313.3	338.6	349.4	360.1	376.5	389.4	396.9	400.8	396.9
125°	242.2	276.5	307.2	331.9	341.7	351.5	365.8	376.2	382.9	385.1	382.9
127.5°	237.9	270.8	300.4	325.1	334.4	343.6	357.9	367.2	372.9	375.1	372.9
130°	234.0	263.6	291.9	316.1	325.6	335.1	349.7	358.7	364.4	366.5	364.4
132.5°	230.4	256.1	282.2	305.8	315.2	324.7	339.0	349.4	354.7	356.9	354.7
135°	226.8	249.3	272.6	294.4	303.3	312.2	326.5	336.5	342.2	344.4	342.2
137.5°	223.6	242.9	263.3	282.2	290.4	298.6	312.2	322.6	327.2	329.7	327.2
140°	221.1	237.6	254.3	270.4	277.9	285.4	297.9	305.8	310.8	313.6	310.8
142.5°	219.0	232.6	246.8	260.1	266.4	272.6	283.3	290.4	294.7	296.5	294.7
145°	216.5	227.9	240.1	250.8	255.8	260.8	269.7	275.8	279.3	281.1	279.3
147.5°	214.3	224.0	234.0	242.9	247.0	251.1	257.9	263.3	266.1	266.8	266.1
150°	211.8	220.4	228.6	235.8	239.0	242.2	247.9	252.6	254.7	255.1	254.7
152.5°	209.0	216.5	223.3	229.7	232.2	234.7	239.3	242.9	244.0	244.3	244.0
155°	206.1	212.5	218.3	223.6	225.8	227.9	231.5	234.3	235.4	235.4	235.4
157.5°	203.3	208.3	213.3	217.9	219.7	221.5	224.3	226.5	227.2	227.2	227.2
160°	200.0	204.3	208.3	212.2	213.6	215.0	217.2	219.3	219.7	219.7	219.7
162.5°	197.2	200.4	203.6	206.5	207.8	209.0	210.4	212.5	212.9	212.5	212.9
165°	194.0	196.8	199.0	201.5	202.4	203.3	204.7	206.1	205.8	205.4	205.8
167.5°	191.1	193.3	195.0	197.2	197.8	198.3	199.0	200.0	200.0	199.7	200.0
170°	188.3	190.0	191.1	192.5	193.0	193.6	194.3	194.7	194.3	194.3	194.3
172.5°	185.8	187.2	187.9	188.6	189.0	189.3	189.7	190.0	189.7	189.0	189.7
175°	184.0	184.7	185.0	185.8	185.8	185.8	185.8	186.5	185.8	185.0	185.8
177.5°	182.5	182.9	183.3	183.3	183.4	183.6	183.3	183.6	182.9	182.2	182.9
180°	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6
2.5°	2144.0	2132.8	2131.2	2131.2	2113.5	2123.1	2103.8	2083.0	2073.3	2073.3	2055.6
5°	2322.4	2311.2	2299.9	2282.2	2282.2	2272.6	2242.1	2211.5	2189.0	2169.7	2148.8
7.5°	2505.6	2494.4	2462.3	2444.6	2454.2	2434.9	2394.8	2343.3	2304.7	2274.2	2230.8
10°	2704.9	2674.4	2658.3	2648.7	2614.9	2594.0	2547.4	2471.9	2423.7	2383.5	2327.2
12.5°	2867.3	2876.9	2815.8	2820.7	2786.9	2758.0	2685.7	2613.3	2541.0	2484.8	2401.2
15°	3042.5	3013.5	2976.6	2947.6	2936.4	2901.0	2839.9	2743.5	2664.8	2576.4	2481.5
17.5°	3180.7	3158.2	3122.8	3095.5	3071.4	2986.2	2934.8	2849.6	2741.9	2655.1	2539.4
20°	3298.0	3277.1	3227.3	3209.6	3166.2	3105.1	3031.2	2899.4	2803.0	2708.2	2595.7
22.5°	3347.8	3326.9	3283.5	3261.0	3233.7	3174.3	3103.5	2978.2	2859.2	2740.3	2621.4
25°	3306.0	3306.0	3285.1	3277.1	3253.0	3200.0	3127.6	3021.6	2894.6	2766.0	2624.6
27.5°	3103.5	3143.7	3158.2	3166.2	3166.2	3167.8	3118.0	3015.1	2891.4	2766.0	2618.2
30°	2811.0	2878.5	2938.0	2955.7	2986.2	3020.0	3040.9	2991.0	2880.1	2748.3	2600.5
32.5°	2443.0	2529.8	2640.7	2668.0	2709.8	2811.0	2867.3	2888.2	2827.1	2711.4	2553.9
35°	2076.5	2185.8	2253.3	2336.9	2375.5	2524.9	2650.3	2725.8	2711.4	2642.3	2499.2
37.5°	1756.7	1819.4	1901.3	1989.7	2066.9	2209.9	2365.8	2512.1	2571.5	2537.8	2430.1
40°	1449.7	1523.6	1621.7	1694.0	1747.0	1890.1	2083.0	2242.1	2372.3	2393.1	2327.2
42.5°	1232.7	1306.7	1366.1	1444.9	1486.7	1624.9	1795.3	1994.6	2148.8	2230.8	2201.9
45°	1065.6	1110.6	1158.8	1203.8	1255.2	1377.4	1534.9	1753.5	1927.1	2042.8	2054.0
47.5°	919.3	959.5	1001.3	1043.1	1072.0	1166.8	1311.5	1489.9	1679.5	1838.7	1901.3
50°	816.5	835.8	866.3	890.4	924.1	1006.1	1121.8	1276.1	1477.0	1649.0	1731.0
52.5°	715.2	739.3	763.4	784.3	806.8	864.7	970.8	1104.2	1277.7	1454.5	1555.8
55°	630.0	649.3	671.8	686.3	699.1	750.6	830.9	933.8	1083.3	1250.4	1375.8
57.5°	560.9	569.0	588.2	596.3	610.7	652.5	710.4	802.0	922.5	1084.9	1187.7
60°	485.4	501.5	515.9	522.3	533.6	562.5	602.7	687.9	792.4	911.3	1028.6
62.5°	424.3	430.7	442.0	450.0	458.1	488.6	522.3	586.6	665.4	765.0	872.7
65°	368.1	371.3	377.7	388.9	393.8	416.3	435.6	482.2	556.1	631.6	739.3
67.5°	310.2	313.4	321.4	327.9	332.7	347.2	368.1	401.8	442.0	525.6	585.0
70°	265.2	265.2	270.0	273.2	278.0	284.5	295.7	321.4	358.4	411.4	466.1
72.5°	221.8	221.8	221.8	226.6	226.6	231.4	237.9	255.5	281.3	323.1	358.4
75°	172.0	173.6	176.8	176.8	178.4	184.8	189.7	194.5	207.3	234.7	266.8
77.5°	130.2	133.4	135.0	131.8	135.0	135.0	141.4	147.9	154.3	162.3	186.4
80°	96.4	98.0	94.8	96.4	96.4	99.6	102.9	101.3	104.5	114.1	120.5
82.5°	64.3	65.9	65.9	65.9	65.9	70.7	70.7	69.1	70.7	72.3	73.9
85°	40.2	38.6	38.6	40.2	38.6	38.6	40.2	41.8	40.2	41.8	43.4
87.5°	17.7	17.7	17.7	17.7	16.1	16.1	17.7	16.1	17.7	16.1	14.5
90°	7.9	7.5	7.1	7.1	7.1	6.8	6.4	6.1	6.4	5.7	5.0
92.5°	33.9	36.4	41.8	46.2	50.7	64.3	86.1	116.5	140.0	122.5	88.9
95°	98.2	109.3	126.8	144.2	161.5	209.3	264.7	299.4	291.1	219.7	134.3
97.5°	228.6	250.1	274.3	294.4	314.4	353.6	381.2	375.4	311.5	210.4	122.5
100°	341.1	362.9	394.0	407.2	420.5	438.0	430.8	378.7	287.2	186.5	113.6
102.5°	444.0	458.3	474.4	478.0	481.5	470.8	428.3	351.9	256.8	170.4	111.1
105°	509.8	512.6	511.9	504.6	497.3	461.9	400.1	318.3	234.3	162.5	112.5
107.5°	533.7	527.3	511.5	496.5	481.5	432.2	365.4	290.8	219.7	160.4	116.8
110°	528.0	513.0	487.6	468.0	448.3	396.5	334.7	271.1	212.9	161.1	121.8

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	501.2	482.2	452.6	433.0	413.3	365.1	312.2	260.1	209.7	163.3	127.2
115°	468.3	446.9	418.7	401.5	384.4	342.6	298.6	254.0	209.0	166.1	132.9
117.5°	435.5	416.9	391.9	376.9	361.9	327.9	290.8	250.8	208.6	169.0	138.6
120°	409.0	393.3	372.9	360.2	347.6	319.0	285.8	248.3	208.6	172.2	144.7
122.5°	389.4	376.5	360.1	349.4	338.6	313.3	281.5	245.4	208.3	175.4	150.4
125°	376.2	365.8	351.5	341.7	331.9	307.2	276.5	242.2	207.9	178.6	156.1
127.5°	367.2	357.9	343.6	334.4	325.1	300.4	270.8	237.9	207.2	181.1	161.1
130°	358.7	349.7	335.1	325.6	316.1	291.9	263.6	234.0	206.8	184.0	165.8
132.5°	349.4	339.0	324.7	315.2	305.8	282.2	256.1	230.4	206.5	186.5	170.4
135°	336.5	326.5	312.2	303.3	294.4	272.6	249.3	226.8	206.1	189.0	174.3
137.5°	322.6	312.2	298.6	290.4	282.2	263.3	242.9	223.6	206.1	190.4	177.2
140°	305.8	297.9	285.4	277.9	270.4	254.3	237.6	221.1	205.8	192.2	180.0
142.5°	290.4	283.3	272.6	266.4	260.1	246.8	232.6	219.0	205.8	193.6	182.2
145°	275.8	269.7	260.8	255.8	250.8	240.1	227.9	216.5	205.0	194.0	183.6
147.5°	263.3	257.9	251.1	247.0	242.9	234.0	224.0	214.3	204.0	194.3	185.0
150°	252.6	247.9	242.2	239.0	235.8	228.6	220.4	211.8	202.9	194.3	186.1
152.5°	242.9	239.3	234.7	232.2	229.7	223.3	216.5	209.0	201.1	193.6	186.8
155°	234.3	231.5	227.9	225.8	223.6	218.3	212.5	206.1	199.3	192.9	187.2
157.5°	226.5	224.3	221.5	219.7	217.9	213.3	208.3	203.3	197.5	192.2	187.2
160°	219.3	217.2	215.0	213.6	212.2	208.3	204.3	200.0	195.4	191.1	187.2
162.5°	212.5	210.4	209.0	207.8	206.5	203.6	200.4	197.2	193.3	190.0	187.2
165°	206.1	204.7	203.3	202.4	201.5	199.0	196.8	194.0	191.1	188.6	186.5
167.5°	200.0	199.0	198.3	197.8	197.2	195.0	193.3	191.1	189.0	187.2	185.8
170°	194.7	194.3	193.6	193.0	192.5	191.1	190.0	188.3	186.8	185.8	185.0
172.5°	190.0	189.7	189.3	189.0	188.6	187.9	187.2	185.8	184.7	184.3	184.3
175°	186.5	185.8	185.8	185.8	185.8	185.0	184.7	184.0	183.3	183.3	183.6
177.5°	183.6	183.3	183.6	183.4	183.3	183.3	182.9	182.5	182.2	182.2	182.9
180°	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6
2.5°	2046.0	2037.9	2033.1	2031.5	2017.1	2009.0	2004.2	2001.0	1996.2	1983.3	1972.1
5°	2123.1	2100.6	2089.4	2076.5	2054.0	2028.3	2007.4	1994.6	1978.5	1952.8	1928.7
7.5°	2195.5	2161.7	2139.2	2121.5	2083.0	2041.2	2007.4	1980.1	1949.6	1914.2	1880.4
10°	2271.0	2216.4	2187.4	2160.1	2103.8	2049.2	2001.0	1960.8	1917.4	1870.8	1833.8
12.5°	2330.5	2258.1	2226.0	2187.4	2118.3	2054.0	1992.9	1938.3	1882.0	1832.2	1779.2
15°	2399.6	2309.6	2272.6	2222.8	2128.0	2044.4	1965.6	1906.2	1848.3	1774.4	1718.1
17.5°	2439.8	2335.3	2282.2	2238.9	2136.0	2034.7	1943.1	1869.2	1801.7	1727.8	1668.3
20°	2479.9	2361.0	2301.5	2240.5	2118.3	2010.6	1914.2	1825.8	1755.1	1674.7	1613.6
22.5°	2492.8	2354.6	2291.9	2235.6	2107.1	1986.5	1875.6	1785.6	1703.6	1623.3	1554.2
25°	2492.8	2353.0	2279.0	2206.7	2071.7	1947.9	1837.0	1739.0	1647.4	1567.0	1497.9
27.5°	2467.1	2320.8	2243.7	2177.8	2037.9	1904.6	1790.4	1682.8	1594.4	1514.0	1435.2
30°	2434.9	2274.2	2197.1	2118.3	1983.3	1856.3	1732.6	1632.9	1539.7	1448.1	1377.4
32.5°	2394.8	2224.4	2139.2	2058.8	1915.8	1784.0	1669.9	1571.9	1483.5	1388.6	1309.9
35°	2336.9	2150.5	2055.6	1984.9	1846.7	1710.1	1600.8	1504.4	1419.2	1321.1	1235.9
37.5°	2263.0	2083.0	1986.5	1899.7	1756.7	1631.3	1528.5	1435.2	1351.7	1261.7	1166.8
40°	2176.2	1988.1	1904.6	1812.9	1661.9	1542.9	1446.5	1362.9	1279.3	1194.2	1102.5
42.5°	2078.1	1891.7	1798.5	1710.1	1565.4	1448.1	1358.1	1282.6	1205.4	1126.7	1028.6
45°	1960.8	1785.6	1695.6	1612.0	1472.2	1351.7	1269.7	1197.4	1131.5	1051.1	964.3
47.5°	1829.0	1676.3	1584.7	1494.7	1358.1	1253.6	1173.3	1112.2	1055.9	975.6	896.8
50°	1700.4	1549.4	1475.4	1383.8	1258.4	1160.4	1078.4	1027.0	983.6	904.9	834.1
52.5°	1538.1	1424.0	1353.3	1274.5	1154.0	1054.3	990.0	945.0	893.6	832.5	769.9
55°	1395.1	1289.0	1232.7	1158.8	1039.9	951.5	896.8	855.0	814.9	760.2	710.4
57.5°	1232.7	1166.8	1110.6	1046.3	929.0	853.4	805.2	769.9	732.9	687.9	647.7
60°	1062.4	1031.8	977.2	925.8	826.1	760.2	720.0	687.9	652.5	615.6	581.8
62.5°	911.3	893.6	861.5	821.3	728.1	671.8	631.6	607.5	581.8	548.1	515.9
65°	768.2	760.2	729.7	700.7	636.5	586.6	551.3	536.8	507.9	482.2	453.2
67.5°	641.3	631.6	614.0	601.1	546.5	499.8	482.2	462.9	438.8	419.5	395.4
70°	512.7	511.1	499.8	483.8	454.8	421.1	403.4	390.6	366.4	352.0	334.3
72.5°	398.6	406.6	397.0	390.6	371.3	347.2	331.1	323.1	303.8	292.5	279.7
75°	297.3	303.8	308.6	297.3	292.5	281.3	266.8	258.8	249.1	233.0	228.2
77.5°	202.5	217.0	217.0	220.2	221.8	215.4	204.1	197.7	186.4	183.2	176.8
80°	133.4	146.3	147.9	151.1	155.9	155.9	147.9	146.3	135.0	133.4	128.6
82.5°	77.1	88.4	94.8	99.6	98.0	104.5	98.0	96.4	90.0	90.0	86.8
85°	41.8	43.4	46.6	49.8	53.0	56.3	56.3	54.6	53.0	51.4	48.2
87.5°	16.1	16.1	17.7	16.1	17.7	20.9	22.5	22.5	20.9	19.3	16.1
90°	5.0	2.9	2.9	2.9	2.5	2.1	1.1	0.4	1.1	2.1	2.5
92.5°	54.3	32.1	27.5	22.9	16.4	11.1	7.1	5.0	7.1	11.1	16.4
95°	75.7	44.7	37.2	29.6	21.1	16.4	12.9	11.8	12.9	16.4	21.1
97.5°	72.2	47.5	41.1	34.7	27.1	22.9	19.6	19.6	19.6	22.9	27.1
100°	73.2	52.2	46.4	40.7	33.9	29.6	27.1	27.1	27.1	29.6	33.9
102.5°	76.8	58.2	52.8	47.5	41.1	37.2	35.0	34.3	35.0	37.2	41.1
105°	82.9	65.7	60.6	55.4	48.9	44.7	42.9	41.8	42.9	44.7	48.9
107.5°	89.3	73.6	68.4	63.2	57.2	52.5	50.7	50.0	50.7	52.5	57.2
110°	96.8	81.1	76.2	71.4	65.0	60.7	58.9	58.2	58.9	60.7	65.0

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	104.0	88.9	84.1	79.3	72.9	68.9	66.8	66.1	66.8	68.9	72.9
115°	111.5	97.2	92.4	87.5	80.7	77.2	74.7	73.6	74.7	77.2	80.7
117.5°	118.6	105.0	100.0	95.0	88.6	84.7	82.5	81.4	82.5	84.7	88.6
120°	126.1	112.5	107.5	102.5	96.4	92.5	90.0	89.3	90.0	92.5	96.4
122.5°	133.2	119.7	114.8	110.0	103.2	99.7	97.2	96.4	97.2	99.7	103.2
125°	139.7	126.8	121.8	116.8	110.0	106.1	104.0	102.5	104.0	106.1	110.0
127.5°	145.7	133.2	128.2	123.2	116.1	111.8	109.3	108.2	109.3	111.8	116.1
130°	151.8	139.7	134.5	129.3	122.5	117.2	114.3	112.9	114.3	117.2	122.5
132.5°	156.8	144.7	139.8	135.0	127.5	122.5	118.6	117.5	118.6	122.5	127.5
135°	161.5	149.7	145.0	140.4	132.9	126.8	123.2	121.8	123.2	126.8	132.9
137.5°	165.0	154.0	149.5	145.0	137.2	131.5	127.5	126.1	127.5	131.5	137.2
140°	168.6	157.9	153.6	149.3	141.8	135.7	131.8	130.7	131.8	135.7	141.8
142.5°	171.8	161.5	157.4	153.2	146.1	140.4	136.8	135.7	136.8	140.4	146.1
145°	174.0	164.7	160.8	156.8	150.0	145.0	141.5	140.4	141.5	145.0	150.0
147.5°	176.5	167.5	164.0	160.4	154.7	149.3	146.1	145.7	146.1	149.3	154.7
150°	178.3	170.4	167.0	163.6	158.2	154.0	151.1	150.7	151.1	154.0	158.2
152.5°	179.7	172.9	169.9	166.8	162.2	158.2	155.4	155.4	155.4	158.2	162.2
155°	181.1	175.0	172.4	169.7	165.8	162.2	160.0	159.7	160.0	162.2	165.8
157.5°	182.2	176.8	174.6	172.5	169.0	166.1	164.0	164.0	164.0	166.1	169.0
160°	182.9	178.6	176.6	174.7	171.8	169.3	167.9	167.9	167.9	169.3	171.8
162.5°	183.6	179.7	178.2	176.8	174.3	172.2	171.1	171.5	171.1	172.2	174.3
165°	183.6	180.4	179.4	178.3	176.5	174.7	174.0	174.0	174.0	174.7	176.5
167.5°	183.6	181.1	180.2	179.3	178.3	176.8	176.5	176.8	176.5	176.8	178.3
170°	183.3	181.5	181.0	180.4	179.7	178.6	178.3	178.6	178.3	178.6	179.7
172.5°	182.9	181.8	181.4	181.1	180.8	180.0	180.0	180.4	180.0	180.0	180.8
175°	182.5	181.8	181.8	181.8	181.5	181.1	181.1	181.5	181.1	181.1	181.5
177.5°	182.2	181.8	181.8	181.8	181.8	181.5	181.8	182.2	181.8	181.5	181.8
180°	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6
2.5°	1962.4	1959.2	1956.0	1943.1	1931.9	1912.6	1896.5	1890.1	1888.5	1890.1	1885.3
5°	1906.2	1904.6	1893.3	1870.8	1849.9	1827.4	1811.3	1795.3	1785.6	1785.6	1774.4
7.5°	1853.1	1841.9	1832.2	1803.3	1779.2	1748.7	1724.5	1710.1	1702.0	1684.4	1684.4
10°	1796.9	1780.8	1767.9	1740.6	1705.3	1674.7	1644.2	1626.5	1612.0	1599.2	1594.4
12.5°	1740.6	1727.8	1703.6	1674.7	1639.4	1600.8	1568.6	1555.8	1522.0	1494.7	1496.3
15°	1687.6	1658.6	1647.4	1605.6	1563.8	1526.9	1480.2	1443.3	1416.0	1398.3	1375.8
17.5°	1628.1	1599.2	1578.3	1542.9	1488.3	1430.4	1385.4	1335.6	1308.3	1277.7	1263.3
20°	1562.2	1538.1	1522.0	1465.8	1399.9	1330.8	1281.0	1250.4	1219.9	1197.4	1184.5
22.5°	1506.0	1475.4	1456.1	1380.6	1308.3	1239.2	1200.6	1174.9	1149.2	1129.9	1123.4
25°	1433.6	1416.0	1369.3	1303.5	1215.1	1168.4	1134.7	1100.9	1086.5	1073.6	1059.2
27.5°	1374.2	1330.8	1298.6	1211.8	1157.2	1104.2	1070.4	1044.7	1027.0	1014.2	1002.9
30°	1300.2	1260.1	1215.1	1142.7	1092.9	1043.1	1012.5	991.7	972.4	964.3	954.7
32.5°	1223.1	1186.1	1142.7	1084.9	1023.8	985.2	961.1	938.6	925.8	917.7	906.5
35°	1154.0	1107.4	1078.4	1023.8	974.0	930.6	908.1	888.8	874.3	871.1	869.5
37.5°	1080.0	1044.7	1017.4	961.1	919.3	882.4	861.5	840.6	832.5	830.9	824.5
40°	1015.8	985.2	959.5	906.5	861.5	827.7	811.6	798.8	790.8	790.8	789.1
42.5°	959.5	927.4	901.6	853.4	813.3	782.7	765.0	752.2	749.0	750.6	749.0
45°	896.8	869.5	843.8	794.0	760.2	737.7	718.4	712.0	707.2	708.8	710.4
47.5°	837.4	814.9	789.1	749.0	710.4	686.3	675.0	668.6	668.6	668.6	671.8
50°	784.3	758.6	736.1	694.3	659.0	639.7	630.0	622.0	623.6	625.2	626.8
52.5°	721.6	699.1	683.1	641.3	615.6	591.5	580.2	581.8	580.2	580.2	583.4
55°	667.0	644.5	628.4	589.8	564.1	548.1	538.4	533.6	535.2	532.0	538.4
57.5°	605.9	586.6	575.4	538.4	515.9	501.5	493.4	485.4	488.6	487.0	485.4
60°	552.9	530.4	512.7	487.0	467.7	450.0	445.2	437.2	440.4	437.2	435.6
62.5°	491.8	474.1	461.3	435.6	419.5	405.0	393.8	388.9	387.3	382.5	377.7
65°	430.7	421.1	408.2	382.5	366.4	355.2	348.8	343.9	342.3	329.5	315.0
67.5°	374.5	368.1	355.2	335.9	321.4	310.2	300.5	292.5	282.9	273.2	265.2
70°	321.4	311.8	303.8	286.1	273.2	262.0	252.3	242.7	237.9	228.2	225.0
72.5°	270.0	260.4	252.3	236.3	225.0	213.8	210.5	199.3	194.5	192.9	192.9
75°	217.0	208.9	204.1	189.7	180.0	172.0	167.2	163.9	160.7	157.5	152.7
77.5°	165.5	160.7	157.5	147.9	139.8	135.0	133.4	122.1	118.9	115.7	112.5
80°	120.5	118.9	115.7	107.7	104.5	93.2	93.2	90.0	88.4	88.4	88.4
82.5°	82.0	78.8	77.1	69.1	67.5	65.9	64.3	62.7	64.3	62.7	64.3
85°	43.4	41.8	40.2	40.2	40.2	40.2	40.2	40.2	40.2	38.6	40.2
87.5°	16.1	16.1	16.1	16.1	14.5	16.1	16.1	14.5	16.1	16.1	16.1
90°	2.9	2.9	2.9	5.0	5.0	5.7	6.4	6.1	6.4	6.8	7.1
92.5°	22.9	27.5	32.1	54.3	88.9	122.5	140.0	116.5	86.1	64.3	50.7
95°	29.6	37.2	44.7	75.7	134.3	219.7	291.1	299.4	264.7	209.3	161.5
97.5°	34.7	41.1	47.5	72.2	122.5	210.4	311.5	375.4	381.2	353.6	314.4
100°	40.7	46.4	52.2	73.2	113.6	186.5	287.2	378.7	430.8	438.0	420.5
102.5°	47.5	52.8	58.2	76.8	111.1	170.4	256.8	351.9	428.3	470.8	481.5
105°	55.4	60.6	65.7	82.9	112.5	162.5	234.3	318.3	400.1	461.9	497.3
107.5°	63.2	68.4	73.6	89.3	116.8	160.4	219.7	290.8	365.4	432.2	481.5
110°	71.4	76.2	81.1	96.8	121.8	161.1	212.9	271.1	334.7	396.5	448.3

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	79.3	84.1	88.9	104.0	127.2	163.3	209.7	260.1	312.2	365.1	413.3
115°	87.5	92.4	97.2	111.5	132.9	166.1	209.0	254.0	298.6	342.6	384.4
117.5°	95.0	100.0	105.0	118.6	138.6	169.0	208.6	250.8	290.8	327.9	361.9
120°	102.5	107.5	112.5	126.1	144.7	172.2	208.6	248.3	285.8	319.0	347.6
122.5°	110.0	114.8	119.7	133.2	150.4	175.4	208.3	245.4	281.5	313.3	338.6
125°	116.8	121.8	126.8	139.7	156.1	178.6	207.9	242.2	276.5	307.2	331.9
127.5°	123.2	128.2	133.2	145.7	161.1	181.1	207.2	237.9	270.8	300.4	325.1
130°	129.3	134.5	139.7	151.8	165.8	184.0	206.8	234.0	263.6	291.9	316.1
132.5°	135.0	139.8	144.7	156.8	170.4	186.5	206.5	230.4	256.1	282.2	305.8
135°	140.4	145.0	149.7	161.5	174.3	189.0	206.1	226.8	249.3	272.6	294.4
137.5°	145.0	149.5	154.0	165.0	177.2	190.4	206.1	223.6	242.9	263.3	282.2
140°	149.3	153.6	157.9	168.6	180.0	192.2	205.8	221.1	237.6	254.3	270.4
142.5°	153.2	157.4	161.5	171.8	182.2	193.6	205.8	219.0	232.6	246.8	260.1
145°	156.8	160.8	164.7	174.0	183.6	194.0	205.0	216.5	227.9	240.1	250.8
147.5°	160.4	164.0	167.5	176.5	185.0	194.3	204.0	214.3	224.0	234.0	242.9
150°	163.6	167.0	170.4	178.3	186.1	194.3	202.9	211.8	220.4	228.6	235.8
152.5°	166.8	169.9	172.9	179.7	186.8	193.6	201.1	209.0	216.5	223.3	229.7
155°	169.7	172.4	175.0	181.1	187.2	192.9	199.3	206.1	212.5	218.3	223.6
157.5°	172.5	174.6	176.8	182.2	187.2	192.2	197.5	203.3	208.3	213.3	217.9
160°	174.7	176.6	178.6	182.9	187.2	191.1	195.4	200.0	204.3	208.3	212.2
162.5°	176.8	178.2	179.7	183.6	187.2	190.0	193.3	197.2	200.4	203.6	206.5
165°	178.3	179.4	180.4	183.6	186.5	188.6	191.1	194.0	196.8	199.0	201.5
167.5°	179.3	180.2	181.1	183.6	185.8	187.2	189.0	191.1	193.3	195.0	197.2
170°	180.4	181.0	181.5	183.3	185.0	185.8	186.8	188.3	190.0	191.1	192.5
172.5°	181.1	181.4	181.8	182.9	184.3	184.3	184.7	185.8	187.2	187.9	188.6
175°	181.8	181.8	181.8	182.5	183.6	183.3	183.3	184.0	184.7	185.0	185.8
177.5°	181.8	181.8	181.8	182.2	182.9	182.2	182.2	182.5	182.9	183.3	183.3
180°	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6
2.5°	1885.3	1891.7	1883.7	1888.5	1877.2	1875.6	1877.2	1877.2	1878.8	1880.4	1882.0
5°	1779.2	1777.6	1767.9	1761.5	1756.7	1761.5	1764.7	1767.9	1764.7	1767.9	1769.5
7.5°	1679.5	1674.7	1669.9	1658.6	1661.9	1658.6	1668.3	1663.5	1663.5	1671.5	1677.9
10°	1591.1	1581.5	1578.3	1565.4	1555.8	1554.2	1565.4	1570.2	1575.1	1578.3	1591.1
12.5°	1477.0	1462.6	1451.3	1456.1	1428.8	1440.1	1443.3	1436.9	1456.1	1478.6	1465.8
15°	1354.9	1356.5	1334.0	1326.0	1303.5	1309.9	1311.5	1327.6	1343.6	1342.0	1361.3
17.5°	1264.9	1255.2	1235.9	1234.3	1224.7	1229.5	1227.9	1240.8	1235.9	1244.0	1260.1
20°	1181.3	1174.9	1158.8	1152.4	1155.6	1152.4	1154.0	1155.6	1160.4	1178.1	1174.9
22.5°	1115.4	1107.4	1107.4	1099.3	1089.7	1086.5	1094.5	1099.3	1105.8	1109.0	1117.0
25°	1057.5	1051.1	1043.1	1038.3	1030.2	1031.8	1036.7	1043.1	1047.9	1054.3	1060.8
27.5°	998.1	998.1	990.0	988.4	985.2	983.6	990.0	993.3	993.3	998.1	1004.5
30°	951.5	951.5	943.4	941.8	940.2	940.2	945.0	946.6	948.3	953.1	956.3
32.5°	906.5	904.9	901.6	903.3	901.6	903.3	903.3	904.9	908.1	909.7	916.1
35°	864.7	866.3	863.1	863.1	861.5	863.1	866.3	867.9	869.5	872.7	872.7
37.5°	824.5	827.7	826.1	830.9	830.9	830.9	830.9	834.1	834.1	834.1	832.5
40°	789.1	789.1	787.5	790.8	794.0	794.0	795.6	795.6	797.2	797.2	795.6
42.5°	749.0	752.2	757.0	758.6	761.8	760.2	765.0	763.4	765.0	761.8	758.6
45°	712.0	712.0	718.4	724.9	726.5	726.5	726.5	729.7	726.5	721.6	720.0
47.5°	671.8	675.0	678.2	686.3	687.9	687.9	687.9	687.9	684.7	684.7	684.7
50°	631.6	633.2	634.9	638.1	642.9	641.3	641.3	641.3	647.7	641.3	642.9
52.5°	583.4	585.0	586.6	593.1	591.5	591.5	593.1	593.1	597.9	596.3	593.1
55°	535.2	535.2	538.4	538.4	538.4	541.6	543.2	546.5	544.8	546.5	548.1
57.5°	487.0	483.8	482.2	482.2	487.0	485.4	487.0	487.0	493.4	496.6	498.2
60°	430.7	430.7	429.1	419.5	419.5	417.9	422.7	425.9	429.1	443.6	442.0
62.5°	372.9	366.4	360.0	361.6	352.0	356.8	353.6	356.8	366.4	377.7	379.3
65°	315.0	310.2	303.8	302.2	298.9	303.8	302.2	303.8	308.6	315.0	323.1
67.5°	263.6	262.0	258.8	257.2	257.2	257.2	260.4	260.4	262.0	266.8	271.6
70°	225.0	223.4	225.0	221.8	223.4	221.8	223.4	225.0	226.6	228.2	233.0
72.5°	189.7	189.7	189.7	186.4	189.7	188.0	188.0	189.7	191.3	192.9	196.1
75°	151.1	147.9	144.6	141.4	139.8	143.0	144.6	143.0	147.9	154.3	154.3
77.5°	114.1	112.5	112.5	112.5	114.1	112.5	115.7	114.1	115.7	115.7	118.9
80°	88.4	86.8	88.4	88.4	86.8	90.0	88.4	88.4	90.0	91.6	90.0
82.5°	64.3	65.9	64.3	64.3	64.3	67.5	64.3	64.3	64.3	65.9	65.9
85°	40.2	40.2	40.2	40.2	41.8	40.2	41.8	40.2	43.4	41.8	41.8
87.5°	14.5	16.1	17.7	17.7	17.7	17.7	16.1	17.7	19.3	17.7	19.3
90°	7.1	7.1	7.5	7.9	7.5	7.5	7.5	7.9	7.5	7.1	7.1
92.5°	46.2	41.8	36.4	33.9	32.5	32.5	32.5	33.9	36.4	41.8	46.2
95°	144.2	126.8	109.3	98.2	91.8	87.2	91.8	98.2	109.3	126.8	144.2
97.5°	294.4	274.3	250.1	228.6	217.9	209.3	217.9	228.6	250.1	274.3	294.4
100°	407.2	394.0	362.9	341.1	330.4	327.6	330.4	341.1	362.9	394.0	407.2
102.5°	478.0	474.4	458.3	444.0	432.6	430.5	432.6	444.0	458.3	474.4	478.0
105°	504.6	511.9	512.6	509.8	504.8	502.6	504.8	509.8	512.6	511.9	504.6
107.5°	496.5	511.5	527.3	533.7	536.5	536.9	536.5	533.7	527.3	511.5	496.5
110°	468.0	487.6	513.0	528.0	534.4	537.6	534.4	528.0	513.0	487.6	468.0

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	433.0	452.6	482.2	501.2	510.8	516.5	510.8	501.2	482.2	452.6	433.0
115°	401.5	418.7	446.9	468.3	479.7	482.6	479.7	468.3	446.9	418.7	401.5
117.5°	376.9	391.9	416.9	435.5	447.6	449.4	447.6	435.5	416.9	391.9	376.9
120°	360.2	372.9	393.3	409.0	418.3	422.2	418.3	409.0	393.3	372.9	360.2
122.5°	349.4	360.1	376.5	389.4	396.9	400.8	396.9	389.4	376.5	360.1	349.4
125°	341.7	351.5	365.8	376.2	382.9	385.1	382.9	376.2	365.8	351.5	341.7
127.5°	334.4	343.6	357.9	367.2	372.9	375.1	372.9	367.2	357.9	343.6	334.4
130°	325.6	335.1	349.7	358.7	364.4	366.5	364.4	358.7	349.7	335.1	325.6
132.5°	315.2	324.7	339.0	349.4	354.7	356.9	354.7	349.4	339.0	324.7	315.2
135°	303.3	312.2	326.5	336.5	342.2	344.4	342.2	336.5	326.5	312.2	303.3
137.5°	290.4	298.6	312.2	322.6	327.2	329.7	327.2	322.6	312.2	298.6	290.4
140°	277.9	285.4	297.9	305.8	310.8	313.6	310.8	305.8	297.9	285.4	277.9
142.5°	266.4	272.6	283.3	290.4	294.7	296.5	294.7	290.4	283.3	272.6	266.4
145°	255.8	260.8	269.7	275.8	279.3	281.1	279.3	275.8	269.7	260.8	255.8
147.5°	247.0	251.1	257.9	263.3	266.1	266.8	266.1	263.3	257.9	251.1	247.0
150°	239.0	242.2	247.9	252.6	254.7	255.1	254.7	252.6	247.9	242.2	239.0
152.5°	232.2	234.7	239.3	242.9	244.0	244.3	244.0	242.9	239.3	234.7	232.2
155°	225.8	227.9	231.5	234.3	235.4	235.4	235.4	234.3	231.5	227.9	225.8
157.5°	219.7	221.5	224.3	226.5	227.2	227.2	227.2	226.5	224.3	221.5	219.7
160°	213.6	215.0	217.2	219.3	219.7	219.7	219.7	219.3	217.2	215.0	213.6
162.5°	207.8	209.0	210.4	212.5	212.9	212.5	212.9	212.5	210.4	209.0	207.8
165°	202.4	203.3	204.7	206.1	205.8	205.4	205.8	206.1	204.7	203.3	202.4
167.5°	197.8	198.3	199.0	200.0	200.0	199.7	200.0	200.0	199.0	198.3	197.8
170°	193.0	193.6	194.3	194.7	194.3	194.3	194.3	194.7	194.3	193.6	193.0
172.5°	189.0	189.3	189.7	190.0	189.7	189.0	189.7	190.0	189.7	189.3	189.0
175°	185.8	185.8	185.8	186.5	185.8	185.0	185.8	186.5	185.8	185.8	185.8
177.5°	183.4	183.6	183.3	183.6	182.9	182.2	182.9	183.6	183.3	183.6	183.4
180°	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6	1994.6
2.5°	1888.5	1896.5	1893.3	1882.0	1886.9	1896.5	1906.2	1919.0	1927.1	1933.5	1936.7
5°	1777.6	1792.0	1788.8	1788.8	1795.3	1811.3	1827.4	1854.7	1864.4	1875.6	1891.7
7.5°	1679.5	1690.8	1700.4	1703.6	1713.3	1734.2	1755.1	1785.6	1809.7	1822.6	1832.2
10°	1592.8	1600.8	1615.3	1623.3	1632.9	1658.6	1689.2	1721.3	1745.4	1767.9	1780.8
12.5°	1481.9	1514.0	1533.3	1546.1	1559.0	1597.6	1621.7	1657.0	1686.0	1706.9	1726.1
15°	1358.1	1396.7	1407.9	1457.7	1489.9	1520.4	1557.4	1599.2	1626.5	1650.6	1676.3
17.5°	1253.6	1281.0	1293.8	1346.8	1374.2	1422.4	1475.4	1528.5	1570.2	1587.9	1613.6
20°	1187.7	1202.2	1227.9	1245.6	1274.5	1330.8	1388.6	1452.9	1515.6	1533.3	1559.0
22.5°	1120.2	1139.5	1157.2	1181.3	1203.8	1242.4	1300.2	1371.0	1438.5	1470.6	1501.1
25°	1059.2	1078.4	1089.7	1115.4	1136.3	1174.9	1215.1	1287.4	1367.7	1395.1	1443.3
27.5°	1010.9	1022.2	1041.5	1052.7	1076.8	1112.2	1149.2	1203.8	1282.6	1329.2	1375.8
30°	962.7	970.8	986.8	1002.9	1020.6	1044.7	1086.5	1139.5	1211.8	1252.0	1298.6
32.5°	914.5	927.4	937.0	948.3	967.5	996.5	1025.4	1076.8	1134.7	1179.7	1226.3
35°	874.3	879.1	892.0	904.9	917.7	943.4	974.0	1023.8	1075.2	1110.6	1152.4
37.5°	830.9	839.0	848.6	853.4	874.3	890.4	922.5	961.1	1022.2	1044.7	1086.5
40°	797.2	795.6	805.2	813.3	822.9	848.6	867.9	909.7	957.9	993.3	1019.0
42.5°	755.4	755.4	758.6	768.2	781.1	797.2	819.7	855.0	904.9	930.6	961.1
45°	721.6	716.8	718.4	724.9	732.9	749.0	771.5	802.0	851.8	872.7	904.9
47.5°	681.5	676.6	676.6	683.1	689.5	700.7	718.4	753.8	794.0	821.3	845.4
50°	636.5	638.1	636.5	641.3	644.5	655.7	675.0	704.0	740.9	763.4	790.8
52.5°	594.7	591.5	589.8	593.1	599.5	607.5	628.4	654.1	689.5	712.0	736.1
55°	543.2	546.5	546.5	546.5	556.1	559.3	575.4	601.1	636.5	654.1	676.6
57.5°	496.6	495.0	498.2	496.6	504.7	515.9	528.8	548.1	583.4	601.1	622.0
60°	445.2	446.8	448.4	448.4	454.8	466.1	480.6	498.2	527.2	544.8	564.1
62.5°	382.5	390.6	398.6	401.8	411.4	419.5	429.1	448.4	474.1	487.0	504.7
65°	323.1	334.3	345.6	353.6	360.0	368.1	380.9	398.6	419.5	432.3	450.0
67.5°	271.6	279.7	294.1	302.2	315.0	324.7	332.7	347.2	372.9	377.7	392.2
70°	234.7	237.9	244.3	250.7	265.2	273.2	282.9	297.3	316.6	327.9	335.9
72.5°	197.7	199.3	202.5	208.9	215.4	225.0	236.3	249.1	266.8	271.6	282.9
75°	157.5	167.2	167.2	172.0	176.8	181.6	191.3	204.1	215.4	223.4	229.8
77.5°	117.3	122.1	125.4	133.4	139.8	144.6	151.1	160.7	167.2	173.6	178.4
80°	91.6	93.2	94.8	94.8	98.0	104.5	110.9	117.3	125.4	128.6	133.4
82.5°	67.5	67.5	67.5	70.7	72.3	73.9	73.9	77.1	85.2	88.4	93.2
85°	43.4	43.4	43.4	43.4	45.0	46.6	48.2	49.8	49.8	49.8	53.0
87.5°	17.7	20.9	19.3	20.9	20.9	20.9	20.9	22.5	22.5	24.1	24.1
90°	7.1	6.8	6.4	6.1	6.4	5.7	5.0	5.0	2.9	2.9	2.9
92.5°	50.7	64.3	86.1	116.5	140.0	122.5	88.9	54.3	32.1	27.5	22.9
95°	161.5	209.3	264.7	299.4	291.1	219.7	134.3	75.7	44.7	37.2	29.6
97.5°	314.4	353.6	381.2	375.4	311.5	210.4	122.5	72.2	47.5	41.1	34.7
100°	420.5	438.0	430.8	378.7	287.2	186.5	113.6	73.2	52.2	46.4	40.7
102.5°	481.5	470.8	428.3	351.9	256.8	170.4	111.1	76.8	58.2	52.8	47.5
105°	497.3	461.9	400.1	318.3	234.3	162.5	112.5	82.9	65.7	60.6	55.4
107.5°	481.5	432.2	365.4	290.8	219.7	160.4	116.8	89.3	73.6	68.4	63.2
110°	448.3	396.5	334.7	271.1	212.9	161.1	121.8	96.8	81.1	76.2	71.4

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	413.3	365.1	312.2	260.1	209.7	163.3	127.2	104.0	88.9	84.1	79.3
115°	384.4	342.6	298.6	254.0	209.0	166.1	132.9	111.5	97.2	92.4	87.5
117.5°	361.9	327.9	290.8	250.8	208.6	169.0	138.6	118.6	105.0	100.0	95.0
120°	347.6	319.0	285.8	248.3	208.6	172.2	144.7	126.1	112.5	107.5	102.5
122.5°	338.6	313.3	281.5	245.4	208.3	175.4	150.4	133.2	119.7	114.8	110.0
125°	331.9	307.2	276.5	242.2	207.9	178.6	156.1	139.7	126.8	121.8	116.8
127.5°	325.1	300.4	270.8	237.9	207.2	181.1	161.1	145.7	133.2	128.2	123.2
130°	316.1	291.9	263.6	234.0	206.8	184.0	165.8	151.8	139.7	134.5	129.3
132.5°	305.8	282.2	256.1	230.4	206.5	186.5	170.4	156.8	144.7	139.8	135.0
135°	294.4	272.6	249.3	226.8	206.1	189.0	174.3	161.5	149.7	145.0	140.4
137.5°	282.2	263.3	242.9	223.6	206.1	190.4	177.2	165.0	154.0	149.5	145.0
140°	270.4	254.3	237.6	221.1	205.8	192.2	180.0	168.6	157.9	153.6	149.3
142.5°	260.1	246.8	232.6	219.0	205.8	193.6	182.2	171.8	161.5	157.4	153.2
145°	250.8	240.1	227.9	216.5	205.0	194.0	183.6	174.0	164.7	160.8	156.8
147.5°	242.9	234.0	224.0	214.3	204.0	194.3	185.0	176.5	167.5	164.0	160.4
150°	235.8	228.6	220.4	211.8	202.9	194.3	186.1	178.3	170.4	167.0	163.6
152.5°	229.7	223.3	216.5	209.0	201.1	193.6	186.8	179.7	172.9	169.9	166.8
155°	223.6	218.3	212.5	206.1	199.3	192.9	187.2	181.1	175.0	172.4	169.7
157.5°	217.9	213.3	208.3	203.3	197.5	192.2	187.2	182.2	176.8	174.6	172.5
160°	212.2	208.3	204.3	200.0	195.4	191.1	187.2	182.9	178.6	176.6	174.7
162.5°	206.5	203.6	200.4	197.2	193.3	190.0	187.2	183.6	179.7	178.2	176.8
165°	201.5	199.0	196.8	194.0	191.1	188.6	186.5	183.6	180.4	179.4	178.3
167.5°	197.2	195.0	193.3	191.1	189.0	187.2	185.8	183.6	181.1	180.2	179.3
170°	192.5	191.1	190.0	188.3	186.8	185.8	185.0	183.3	181.5	181.0	180.4
172.5°	188.6	187.9	187.2	185.8	184.7	184.3	184.3	182.9	181.8	181.4	181.1
175°	185.8	185.0	184.7	184.0	183.3	183.3	183.6	182.5	181.8	181.8	181.8
177.5°	183.3	183.3	182.9	182.5	182.2	182.2	182.9	182.2	181.8	181.8	181.8
180°	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1994.6	1994.6	1994.6	1994.6
2.5°	1949.6	1959.2	1975.3	1997.8
5°	1904.6	1931.9	1957.6	1991.3
7.5°	1864.4	1896.5	1931.9	1980.1
10°	1817.8	1857.9	1902.9	1962.4
12.5°	1763.1	1819.4	1870.8	1935.1
15°	1722.9	1764.7	1830.6	1906.2
17.5°	1666.7	1722.9	1788.8	1874.0
20°	1613.6	1673.1	1747.0	1835.4
22.5°	1557.4	1624.9	1698.8	1793.7
25°	1499.5	1571.9	1645.8	1747.0
27.5°	1446.5	1512.4	1596.0	1698.8
30°	1382.2	1457.7	1538.1	1645.8
32.5°	1319.5	1398.3	1480.2	1587.9
35°	1252.0	1330.8	1420.8	1523.6
37.5°	1186.1	1272.9	1354.9	1454.5
40°	1113.8	1203.8	1289.0	1390.2
42.5°	1043.1	1136.3	1221.5	1308.3
45°	977.2	1068.8	1145.9	1227.9
47.5°	914.5	996.5	1075.2	1149.2
50°	853.4	922.5	994.9	1055.9
52.5°	789.1	855.0	912.9	967.5
55°	731.3	782.7	834.1	884.0
57.5°	662.2	713.6	758.6	797.2
60°	604.3	636.5	679.9	720.0
62.5°	538.4	575.4	609.1	634.9
65°	474.1	506.3	532.0	554.5
67.5°	419.5	438.8	458.1	482.2
70°	353.6	369.7	392.2	409.8
72.5°	297.3	310.2	321.4	342.3
75°	241.1	252.3	258.8	278.0
77.5°	186.4	197.7	202.5	213.8
80°	143.0	144.6	151.1	160.7
82.5°	98.0	101.3	102.9	110.9
85°	56.3	64.3	62.7	65.9
87.5°	24.1	25.7	28.9	32.1
90°	2.5	2.1	1.1	0.4
92.5°	16.4	11.1	7.1	5.0
95°	21.1	16.4	12.9	11.8
97.5°	27.1	22.9	19.6	19.6
100°	33.9	29.6	27.1	27.1
102.5°	41.1	37.2	35.0	34.3
105°	48.9	44.7	42.9	41.8
107.5°	57.2	52.5	50.7	50.0
110°	65.0	60.7	58.9	58.2

TEST NUMBER: P1026153

CATALOG NUMBER: S124RDIP-B1195D365UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	72.9	68.9	66.8	66.1
115°	80.7	77.2	74.7	73.6
117.5°	88.6	84.7	82.5	81.4
120°	96.4	92.5	90.0	89.3
122.5°	103.2	99.7	97.2	96.4
125°	110.0	106.1	104.0	102.5
127.5°	116.1	111.8	109.3	108.2
130°	122.5	117.2	114.3	112.9
132.5°	127.5	122.5	118.6	117.5
135°	132.9	126.8	123.2	121.8
137.5°	137.2	131.5	127.5	126.1
140°	141.8	135.7	131.8	130.7
142.5°	146.1	140.4	136.8	135.7
145°	150.0	145.0	141.5	140.4
147.5°	154.7	149.3	146.1	145.7
150°	158.2	154.0	151.1	150.7
152.5°	162.2	158.2	155.4	155.4
155°	165.8	162.2	160.0	159.7
157.5°	169.0	166.1	164.0	164.0
160°	171.8	169.3	167.9	167.9
162.5°	174.3	172.2	171.1	171.5
165°	176.5	174.7	174.0	174.0
167.5°	178.3	176.8	176.5	176.8
170°	179.7	178.6	178.3	178.6
172.5°	180.8	180.0	180.0	180.4
175°	181.5	181.1	181.1	181.5
177.5°	181.8	181.5	181.8	182.2
180°	181.8	181.8	181.8	181.8

(END OF REPORT)