

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026165

Luminaire Tested: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026165
REPORT IS A COMBINATION OF REPORTS P999135 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6095.0 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot





TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	79								
1	105	101	97	94	100	97	93	90	89	86	84	81	79	77	75	73	72	68								
2	96	89	83	78	92	85	80	75	79	74	70	72	69	66	67	64	61	58								
3	88	79	72	66	84	76	69	64	70	65	60	65	60	57	60	56	53	50								
4	81	70	62	56	77	68	60	55	63	57	52	58	53	49	54	50	46	44								
5	75	63	55	49	71	61	53	48	57	50	45	52	47	43	49	44	41	38								
6	69	57	49	43	66	55	48	42	51	45	40	48	42	38	44	40	36	34								
7	64	52	44	38	61	50	43	37	47	40	36	44	38	34	41	36	32	30								
8	60	47	40	34	57	46	38	33	43	37	32	40	35	31	37	33	29	27								
9	56	44	36	31	54	42	35	30	40	33	29	37	32	28	35	30	27	25								
10	53	40	33	28	50	39	32	27	37	30	26	34	29	25	32	28	24	22								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15571	15571	15571	15571
5°	15571	17595	15596	13448
10°	15488	20283	15476	11695
15°	15304	22827	15304	9791
20°	15111	24749	15031	8622
25°	14875	24855	14807	7787
30°	14625	21135	14511	7213
35°	14271	15947	14090	6786
40°	13877	11557	13604	6451
45°	13227	8783	12897	6155
50°	12453	7098	12112	5722
55°	11617	5878	11237	5145
60°	10775	4970	10295	4279
65°	9721	4049	9411	3401
70°	8754	3282	8342	2762
75°	7671	2366	7138	2024
80°	6330	1568	5758	1489
85°	4592	807	3806	807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 19493 cd/sqm

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.9	3.0
10°-20°	558.4	9.2
20°-30°	874.6	14.4
30°-40°	971.3	15.9
40°-50°	860.7	14.1
50°-60°	670.7	11.0
60°-70°	438.7	7.2
70°-80°	215.3	3.5
80°-90°	53.1	0.9
90°-100°	126.1	2.1
100°-110°	263.3	4.3
110°-120°	234.0	3.8
120°-130°	197.0	3.2
130°-140°	164.4	2.7
140°-150°	125.5	2.1
150°-160°	88.2	1.4
160°-170°	51.9	0.9
170°-180°	16.9	0.3
0°-30°	1617.9	26.5
0°-40°	2589.2	42.5
0°-60°	4120.5	67.6
0°-90°	4827.7	79.2
90°-120°	623.4	10.2
90°-150°	1110.3	18.2
90°-180°	1267.0	20.8
0°-180°	6095.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1910	1910	1910	1910	1910	
5°	1906	2206	1910	1686	1906	181
15°	1825	2924	1825	1254	1825	515
25°	1672	3153	1665	988	1672	771
35°	1459	1942	1440	826	1459	912
45°	1176	992	1146	696	1176	907
55°	846	592	819	518	846	757
65°	531	346	514	291	531	529
75°	266	160	248	137	266	282
85°	63	38	52	38	63	71
90°	0	7	0	7	0	5
95°	11	83	11	83	11	12
105°	40	481	40	481	40	43
115°	70	462	70	462	70	70
125°	98	368	98	368	98	87
135°	117	330	117	330	117	90
145°	134	269	134	269	134	84
155°	153	225	153	225	153	70
165°	166	197	166	197	166	47
175°	174	177	174	177	174	16
180°	174	174	174	174	174	

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5
2.5°	1912.6	1929.5	1938.7	1946.4	1961.8	1968.0	1980.3	1983.4	1995.7	1994.1	1989.5
5°	1906.4	1935.7	1957.2	1980.3	2008.0	2023.4	2040.3	2064.9	2077.2	2094.1	2104.9
7.5°	1895.7	1935.7	1971.1	2006.4	2051.1	2075.7	2097.2	2135.7	2168.0	2195.7	2226.5
10°	1878.7	1929.5	1981.8	2029.5	2091.1	2120.3	2152.6	2209.5	2254.2	2292.6	2341.9
12.5°	1852.6	1923.4	1981.8	2046.4	2124.9	2164.9	2208.0	2275.7	2328.0	2391.1	2452.7
15°	1824.9	1903.3	1980.3	2064.9	2154.2	2200.3	2243.4	2334.2	2414.2	2486.5	2554.2
17.5°	1794.1	1880.3	1964.9	2058.8	2166.5	2223.4	2274.2	2383.4	2471.1	2565.0	2632.7
20°	1757.2	1851.0	1948.0	2052.6	2174.2	2237.2	2294.2	2418.8	2515.7	2617.3	2701.9
22.5°	1717.2	1818.7	1924.9	2038.8	2164.9	2234.2	2300.3	2434.2	2546.5	2640.4	2754.2
25°	1672.5	1780.3	1889.5	2009.5	2151.1	2226.5	2294.2	2426.5	2546.5	2669.6	2780.4
27.5°	1626.4	1737.2	1851.0	1977.2	2121.8	2195.7	2272.6	2400.3	2540.4	2674.2	2786.6
30°	1575.6	1683.3	1803.3	1923.4	2077.2	2151.1	2229.5	2368.0	2520.4	2654.2	2775.8
32.5°	1520.2	1631.0	1744.9	1869.5	2020.3	2100.3	2172.6	2329.6	2485.0	2617.3	2731.2
35°	1458.7	1563.3	1671.0	1798.7	1948.0	2020.3	2106.5	2269.6	2426.5	2566.5	2640.4
37.5°	1392.5	1492.5	1592.5	1718.7	1861.8	1949.5	2034.1	2198.8	2365.0	2458.8	2497.3
40°	1331.0	1418.7	1506.4	1627.9	1772.6	1863.3	1949.5	2120.3	2266.5	2338.8	2309.6
42.5°	1252.5	1343.3	1421.7	1534.1	1680.2	1764.9	1852.6	2029.5	2148.0	2177.2	2104.9
45°	1175.6	1250.9	1326.3	1435.6	1589.5	1661.8	1755.6	1920.3	2018.7	1992.6	1886.4
47.5°	1100.2	1161.7	1232.5	1338.7	1477.1	1563.3	1651.0	1794.1	1863.3	1826.4	1678.7
50°	1010.9	1072.5	1146.3	1238.6	1372.5	1455.6	1524.8	1657.2	1709.5	1618.7	1440.2
52.5°	926.3	980.1	1043.2	1129.4	1257.1	1332.5	1407.9	1521.8	1538.7	1434.1	1246.3
55°	846.3	889.4	955.5	1024.8	1141.7	1221.7	1274.0	1371.0	1366.3	1235.6	1074.0
57.5°	763.2	803.2	847.8	920.1	1030.9	1090.9	1147.9	1232.5	1187.9	1077.1	917.1
60°	689.3	712.4	757.0	826.3	920.1	972.4	1017.1	1063.2	1024.8	904.7	781.6
62.5°	607.8	633.9	666.2	721.6	804.7	854.0	886.3	906.3	866.3	774.0	661.6
65°	530.8	553.9	587.8	637.0	700.1	737.0	754.0	767.8	746.3	641.6	552.4
67.5°	461.6	477.0	507.8	540.1	607.8	617.0	640.1	646.2	603.2	523.2	452.4
70°	392.4	407.8	421.6	460.1	490.8	507.8	512.4	512.4	469.3	417.0	358.5
72.5°	327.7	337.0	350.8	377.0	393.9	406.2	412.4	404.7	364.7	321.6	278.5
75°	266.2	270.8	283.1	300.0	313.9	309.3	307.7	298.5	269.3	238.5	213.9
77.5°	204.6	207.7	221.6	226.2	226.2	230.8	224.6	215.4	190.8	167.7	156.9
80°	153.9	158.5	160.0	163.1	160.0	160.0	155.4	140.0	127.7	116.9	109.2
82.5°	106.2	109.2	110.8	106.2	109.2	104.6	96.9	86.2	78.5	76.9	73.9
85°	63.1	64.6	63.1	63.1	58.5	56.9	50.8	49.2	46.2	46.2	44.6
87.5°	30.8	29.2	26.2	23.1	23.1	21.5	23.1	20.0	23.1	21.5	20.0
90°	0.3	1.0	2.1	2.4	2.7	2.7	2.7	4.8	4.8	5.5	6.2
92.5°	4.8	6.8	10.6	15.7	21.9	26.4	30.8	52.0	85.1	117.3	134.0
95°	11.3	12.3	15.7	20.2	28.4	35.6	42.7	72.5	128.5	210.2	278.6
97.5°	18.8	18.8	21.9	26.0	33.2	39.4	45.5	69.1	117.3	201.4	298.1
100°	26.0	26.0	28.4	32.5	39.0	44.4	49.9	70.1	108.7	178.4	274.9
102.5°	32.8	33.5	35.6	39.3	45.5	50.6	55.7	73.5	106.3	163.1	245.8
105°	40.0	41.0	42.7	46.8	53.0	58.0	62.9	79.3	107.7	155.5	224.3
107.5°	47.9	48.5	50.3	54.7	60.5	65.4	70.4	85.5	111.8	153.5	210.2
110°	55.7	56.4	58.1	62.2	68.4	73.0	77.6	92.6	116.6	154.2	203.7

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	63.2	63.9	66.0	69.7	75.9	80.5	85.1	99.5	121.7	156.2	200.7
115°	70.4	71.4	73.8	77.3	83.8	88.4	93.0	106.7	127.2	159.0	200.0
117.5°	77.9	79.0	81.0	84.8	90.9	95.7	100.5	113.5	132.6	161.7	199.6
120°	85.5	86.1	88.5	92.3	98.1	102.9	107.7	120.7	138.5	164.8	199.6
122.5°	92.3	93.0	95.4	98.8	105.3	109.9	114.5	127.5	143.9	167.9	199.3
125°	98.1	99.5	101.5	105.3	111.8	116.6	121.4	133.7	149.4	170.9	199.0
127.5°	103.6	104.6	107.0	111.1	117.9	122.7	127.5	139.5	154.2	173.3	198.3
130°	108.0	109.4	112.1	117.3	123.8	128.8	133.7	145.3	158.6	176.1	197.9
132.5°	112.5	113.5	117.3	122.0	129.2	133.8	138.5	150.1	163.1	178.4	197.6
135°	116.6	117.9	121.4	127.2	134.3	138.8	143.2	154.5	166.8	180.8	197.3
137.5°	120.7	122.0	125.8	131.3	138.8	143.0	147.3	157.9	169.6	182.2	197.3
140°	125.1	126.1	129.9	135.7	142.9	147.0	151.1	161.4	172.3	183.9	196.9
142.5°	129.9	130.9	134.3	139.8	146.7	150.6	154.5	164.4	174.3	185.3	196.9
145°	134.3	135.4	138.8	143.6	150.1	153.8	157.6	166.5	175.7	185.6	196.2
147.5°	139.5	139.8	142.9	148.0	153.5	156.9	160.3	168.9	177.1	186.0	195.2
150°	144.3	144.6	147.3	151.4	156.6	159.8	163.1	170.6	178.1	186.0	194.2
152.5°	148.7	148.7	151.4	155.2	159.6	162.6	165.5	172.0	178.8	185.3	192.5
155°	152.8	153.2	155.2	158.6	162.4	165.0	167.5	173.3	179.1	184.6	190.8
157.5°	156.9	156.9	159.0	161.7	165.1	167.1	169.2	174.3	179.1	183.9	189.0
160°	160.7	160.7	162.0	164.4	167.2	169.0	170.9	175.0	179.1	182.9	187.0
162.5°	164.1	163.7	164.8	166.8	169.2	170.6	172.0	175.7	179.1	181.9	184.9
165°	166.5	166.5	167.2	168.9	170.6	171.6	172.6	175.7	178.4	180.5	182.9
167.5°	169.2	168.9	169.2	170.6	171.6	172.4	173.3	175.7	177.8	179.1	180.8
170°	170.9	170.6	170.9	172.0	172.6	173.1	173.7	175.4	177.1	177.8	178.8
172.5°	172.6	172.3	172.3	173.0	173.3	173.6	174.0	175.0	176.4	176.4	176.7
175°	173.7	173.3	173.3	173.7	174.0	174.0	174.0	174.7	175.7	175.4	175.4
177.5°	174.3	174.0	173.7	174.0	174.0	174.0	174.0	174.3	175.0	174.3	174.3
180°	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5
2.5°	2001.8	2018.7	2020.3	2035.7	2031.1	2023.4	2037.2	2028.0	2046.4	2040.3	2048.0
5°	2118.8	2141.8	2161.8	2174.2	2195.7	2191.1	2214.2	2206.5	2223.4	2206.5	2228.0
7.5°	2255.7	2294.2	2314.2	2346.5	2355.7	2357.3	2385.0	2391.1	2401.9	2391.1	2403.4
10°	2389.6	2435.7	2481.9	2508.1	2525.0	2548.1	2572.7	2583.4	2591.1	2580.4	2588.1
12.5°	2511.1	2583.4	2634.2	2686.5	2698.8	2718.8	2745.0	2741.9	2772.7	2766.5	2780.4
15°	2623.5	2703.5	2765.0	2806.6	2840.4	2857.3	2906.6	2909.6	2908.1	2923.5	2914.3
17.5°	2723.5	2791.2	2878.9	2932.7	2974.3	2974.3	3002.0	3058.9	3054.3	3052.7	3062.0
20°	2805.0	2881.9	2963.5	3054.3	3088.1	3094.3	3132.8	3162.0	3166.6	3166.6	3166.6
22.5°	2866.6	2957.3	3045.0	3109.7	3135.8	3157.4	3191.2	3209.7	3215.8	3212.8	3215.8
25°	2897.3	2983.5	3072.7	3131.2	3146.6	3158.9	3162.0	3172.8	3171.2	3152.8	3163.5
27.5°	2903.5	2986.6	3045.0	3060.4	3052.7	3045.0	2995.8	3000.4	2986.6	2958.9	2969.7
30°	2875.8	2920.4	2918.9	2871.2	2857.3	2825.0	2780.4	2714.2	2660.4	2637.3	2645.0
32.5°	2775.8	2775.8	2720.4	2612.7	2565.0	2506.5	2426.5	2366.5	2295.7	2280.3	2309.6
35°	2637.3	2558.8	2457.3	2315.7	2243.4	2200.3	2061.8	2018.7	1958.7	1941.8	1955.7
37.5°	2421.9	2291.1	2143.4	2011.1	1949.5	1872.6	1751.0	1689.5	1646.4	1617.2	1631.0
40°	2180.3	2021.8	1868.0	1704.9	1637.2	1574.1	1483.3	1427.9	1358.7	1361.7	1366.3
42.5°	1949.5	1763.3	1591.0	1440.2	1375.6	1323.3	1260.2	1192.5	1167.9	1160.2	1152.5
45°	1704.9	1506.4	1344.8	1232.5	1174.0	1124.8	1066.3	1027.8	998.6	992.4	1000.1
47.5°	1474.1	1306.3	1152.5	1047.8	1000.1	975.5	929.4	894.0	875.5	860.1	869.4
50°	1264.8	1107.9	984.8	897.1	863.2	846.3	803.2	784.7	766.3	761.6	760.1
52.5°	1092.5	958.6	852.4	781.6	755.5	746.3	713.9	687.8	672.4	677.0	680.1
55°	935.5	821.7	738.6	681.6	660.1	649.3	626.2	607.8	597.0	592.4	595.5
57.5°	797.0	698.6	638.6	592.4	575.5	570.9	546.2	540.1	532.4	527.8	527.8
60°	670.9	601.6	546.2	520.1	501.6	497.0	478.5	470.8	469.3	464.7	461.6
62.5°	564.7	507.8	469.3	441.6	433.9	432.4	420.1	410.8	406.2	403.1	403.1
65°	472.4	430.8	398.5	378.5	372.4	369.3	355.4	352.4	349.3	346.2	344.7
67.5°	393.9	357.0	333.9	320.0	312.4	313.9	306.2	300.0	300.0	298.5	297.0
70°	318.5	295.4	275.4	267.7	264.7	261.6	258.5	253.9	252.3	252.3	252.3
72.5°	250.8	235.4	224.6	220.0	217.0	213.9	210.8	210.8	210.8	209.3	209.3
75°	192.3	186.2	178.5	173.9	173.9	176.9	172.3	167.7	163.1	160.0	161.6
77.5°	144.6	141.6	136.9	129.2	130.8	127.7	127.7	124.6	126.2	126.2	123.1
80°	106.2	101.6	100.0	95.4	96.9	95.4	93.9	93.9	90.8	90.8	90.8
82.5°	73.9	69.2	69.2	67.7	66.2	66.2	64.6	64.6	66.2	63.1	63.1
85°	44.6	43.1	43.1	40.0	40.0	40.0	40.0	41.5	40.0	38.5	38.5
87.5°	20.0	21.5	20.0	18.5	18.5	18.5	16.9	16.9	15.4	16.9	16.9
90°	5.8	6.2	6.5	6.8	6.8	6.8	7.2	7.5	7.2	7.2	7.2
92.5°	111.4	82.4	61.5	48.5	44.2	40.0	34.9	32.5	31.1	31.1	31.1
95°	286.5	253.3	200.3	154.5	138.0	121.4	104.6	94.0	87.9	83.4	87.9
97.5°	359.3	364.8	338.4	300.8	281.6	262.5	239.3	218.8	208.5	200.3	208.5
100°	362.4	412.3	419.1	402.4	389.8	377.1	347.3	326.5	316.2	313.5	316.2
102.5°	336.7	409.9	450.6	460.8	457.4	454.0	438.6	424.9	414.0	411.9	414.0
105°	304.6	382.9	442.0	475.9	482.9	489.9	490.6	487.8	483.0	481.0	483.0
107.5°	278.3	349.7	413.6	460.8	475.2	489.5	504.6	510.7	513.5	513.8	513.5
110°	259.5	320.3	379.5	429.0	447.8	466.6	490.9	505.3	511.4	514.5	511.4

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	248.9	298.8	349.4	395.5	414.3	433.1	461.5	479.6	488.9	494.3	488.9
115°	243.1	285.8	327.8	367.8	384.2	400.7	427.7	448.2	459.1	461.8	459.1
117.5°	240.0	278.3	313.8	346.3	360.6	375.0	398.9	416.7	428.3	430.1	428.3
120°	237.6	273.5	305.3	332.6	344.8	356.9	376.4	391.4	400.3	404.1	400.3
122.5°	234.9	269.4	299.8	324.1	334.4	344.6	360.3	372.6	379.8	383.6	379.8
125°	231.8	264.6	294.0	317.6	327.0	336.4	350.1	360.0	366.5	368.5	366.5
127.5°	227.7	259.1	287.5	311.1	320.0	328.9	342.5	351.4	356.9	358.9	356.9
130°	223.9	252.3	279.3	302.5	311.6	320.7	334.7	343.2	348.7	350.7	348.7
132.5°	220.5	245.1	270.1	292.6	301.6	310.7	324.4	334.3	339.5	341.5	339.5
135°	217.1	238.6	260.8	281.7	290.2	298.8	312.5	322.0	327.5	329.5	327.5
137.5°	214.0	232.5	251.9	270.1	278.0	285.8	298.8	308.7	313.1	315.5	313.1
140°	211.6	227.3	243.4	258.8	266.0	273.1	285.1	292.6	297.4	300.1	297.4
142.5°	209.6	222.5	236.2	248.9	254.8	260.8	271.1	277.9	282.0	283.7	282.0
145°	207.2	218.1	229.7	240.0	244.8	249.6	258.1	263.9	267.3	269.0	267.3
147.5°	205.1	214.3	223.9	232.5	236.4	240.3	246.8	251.9	254.7	255.4	254.7
150°	202.7	210.9	218.8	225.6	228.7	231.8	237.2	241.7	243.7	244.1	243.7
152.5°	200.0	207.2	213.7	219.8	222.2	224.6	229.0	232.5	233.5	233.8	233.5
155°	197.3	203.4	208.9	214.0	216.0	218.1	221.5	224.3	225.3	225.3	225.3
157.5°	194.5	199.3	204.1	208.5	210.2	211.9	214.7	216.7	217.4	217.4	217.4
160°	191.4	195.5	199.3	203.1	204.4	205.8	207.8	209.9	210.2	210.2	210.2
162.5°	188.7	191.8	194.9	197.6	198.8	200.0	201.4	203.4	203.7	203.4	203.7
165°	185.6	188.4	190.4	192.8	193.6	194.5	195.9	197.3	196.9	196.6	196.9
167.5°	182.9	184.9	186.7	188.7	189.2	189.7	190.4	191.4	191.4	191.1	191.4
170°	180.2	181.9	182.9	184.3	184.8	185.3	186.0	186.3	186.0	186.0	186.0
172.5°	177.8	179.1	179.8	180.5	180.8	181.2	181.5	181.9	181.5	180.8	181.5
175°	176.1	176.7	177.1	177.8	177.8	177.8	177.8	178.4	177.8	177.1	177.8
177.5°	174.7	175.0	175.4	175.4	175.6	175.7	175.4	175.7	175.0	174.3	175.0
180°	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5
2.5°	2052.6	2041.8	2040.3	2040.3	2023.4	2032.6	2014.1	1994.1	1984.9	1984.9	1968.0
5°	2223.4	2212.6	2201.9	2184.9	2184.9	2175.7	2146.5	2117.2	2095.7	2077.2	2057.2
7.5°	2398.8	2388.0	2357.3	2340.3	2349.6	2331.1	2292.6	2243.4	2206.5	2177.2	2135.7
10°	2589.6	2560.4	2545.0	2535.7	2503.4	2483.4	2438.8	2366.5	2320.3	2281.9	2228.0
12.5°	2745.0	2754.2	2695.8	2700.4	2668.1	2640.4	2571.1	2501.9	2432.7	2378.8	2298.8
15°	2912.7	2885.0	2849.6	2821.9	2811.2	2777.3	2718.8	2626.5	2551.1	2466.5	2375.7
17.5°	3045.0	3023.5	2989.7	2963.5	2940.4	2858.9	2809.6	2728.1	2625.0	2541.9	2431.1
20°	3157.4	3137.4	3089.7	3072.7	3031.2	2972.7	2902.0	2775.8	2683.5	2592.7	2485.0
22.5°	3205.1	3185.1	3143.5	3122.0	3095.8	3038.9	2971.2	2851.2	2737.3	2623.5	2509.6
25°	3165.1	3165.1	3145.1	3137.4	3114.3	3063.5	2994.3	2892.7	2771.2	2648.1	2512.7
27.5°	2971.2	3009.7	3023.5	3031.2	3031.2	3032.7	2985.0	2886.6	2768.1	2648.1	2506.5
30°	2691.2	2755.8	2812.7	2829.6	2858.9	2891.2	2911.2	2863.5	2757.3	2631.1	2489.6
32.5°	2338.8	2421.9	2528.1	2554.2	2594.2	2691.2	2745.0	2765.0	2706.5	2595.8	2445.0
35°	1988.0	2092.6	2157.2	2237.2	2274.2	2417.3	2537.3	2609.6	2595.8	2529.6	2392.6
37.5°	1681.8	1741.8	1820.3	1904.9	1978.7	2115.7	2264.9	2405.0	2461.9	2429.6	2326.5
40°	1387.9	1458.7	1552.5	1621.8	1672.5	1809.5	1994.1	2146.5	2271.1	2291.1	2228.0
42.5°	1180.2	1250.9	1307.9	1383.3	1423.3	1555.6	1718.7	1909.5	2057.2	2135.7	2108.0
45°	1020.1	1063.2	1109.4	1152.5	1201.7	1318.6	1469.4	1678.7	1844.9	1955.7	1966.4
47.5°	880.1	918.6	958.6	998.6	1026.3	1117.1	1255.6	1426.4	1607.9	1760.3	1820.3
50°	781.6	800.1	829.3	852.4	884.7	963.2	1074.0	1221.7	1414.0	1578.7	1657.2
52.5°	684.7	707.8	730.9	750.9	772.4	827.8	929.4	1057.1	1223.3	1392.5	1489.4
55°	603.2	621.6	643.2	657.0	669.3	718.6	795.5	894.0	1037.1	1197.1	1317.1
57.5°	537.0	544.7	563.2	570.9	584.7	624.7	680.1	767.8	883.2	1038.6	1137.1
60°	464.7	480.1	493.9	500.1	510.8	538.5	577.0	658.6	758.6	872.4	984.8
62.5°	406.2	412.4	423.1	430.8	438.5	467.8	500.1	561.6	637.0	732.4	835.5
65°	352.4	355.4	361.6	372.4	377.0	398.5	417.0	461.6	532.4	604.7	707.8
67.5°	297.0	300.0	307.7	313.9	318.5	332.4	352.4	384.7	423.1	503.1	560.1
70°	253.9	253.9	258.5	261.6	266.2	272.3	283.1	307.7	343.1	393.9	446.2
72.5°	212.3	212.3	212.3	217.0	217.0	221.6	227.7	244.7	269.3	309.3	343.1
75°	164.6	166.2	169.3	169.3	170.8	176.9	181.6	186.2	198.5	224.6	255.4
77.5°	124.6	127.7	129.2	126.2	129.2	129.2	135.4	141.6	147.7	155.4	178.5
80°	92.3	93.9	90.8	92.3	92.3	95.4	98.5	96.9	100.0	109.2	115.4
82.5°	61.5	63.1	63.1	63.1	63.1	67.7	67.7	66.2	67.7	69.2	70.8
85°	38.5	36.9	36.9	38.5	36.9	36.9	38.5	40.0	38.5	40.0	41.5
87.5°	16.9	16.9	16.9	16.9	15.4	15.4	16.9	15.4	16.9	15.4	13.8
90°	7.5	7.2	6.8	6.8	6.8	6.5	6.2	5.8	6.2	5.5	4.8
92.5°	32.5	34.9	40.0	44.2	48.5	61.5	82.4	111.4	134.0	117.3	85.1
95°	94.0	104.6	121.4	138.0	154.5	200.3	253.3	286.5	278.6	210.2	128.5
97.5°	218.8	239.3	262.5	281.6	300.8	338.4	364.8	359.3	298.1	201.4	117.3
100°	326.5	347.3	377.1	389.8	402.4	419.1	412.3	362.4	274.9	178.4	108.7
102.5°	424.9	438.6	454.0	457.4	460.8	450.6	409.9	336.7	245.8	163.1	106.3
105°	487.8	490.6	489.9	482.9	475.9	442.0	382.9	304.6	224.3	155.5	107.7
107.5°	510.7	504.6	489.5	475.2	460.8	413.6	349.7	278.3	210.2	153.5	111.8
110°	505.3	490.9	466.6	447.8	429.0	379.5	320.3	259.5	203.7	154.2	116.6

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	479.6	461.5	433.1	414.3	395.5	349.4	298.8	248.9	200.7	156.2	121.7
115°	448.2	427.7	400.7	384.2	367.8	327.8	285.8	243.1	200.0	159.0	127.2
117.5°	416.7	398.9	375.0	360.6	346.3	313.8	278.3	240.0	199.6	161.7	132.6
120°	391.4	376.4	356.9	344.8	332.6	305.3	273.5	237.6	199.6	164.8	138.5
122.5°	372.6	360.3	344.6	334.4	324.1	299.8	269.4	234.9	199.3	167.9	143.9
125°	360.0	350.1	336.4	327.0	317.6	294.0	264.6	231.8	199.0	170.9	149.4
127.5°	351.4	342.5	328.9	320.0	311.1	287.5	259.1	227.7	198.3	173.3	154.2
130°	343.2	334.7	320.7	311.6	302.5	279.3	252.3	223.9	197.9	176.1	158.6
132.5°	334.3	324.4	310.7	301.6	292.6	270.1	245.1	220.5	197.6	178.4	163.1
135°	322.0	312.5	298.8	290.2	281.7	260.8	238.6	217.1	197.3	180.8	166.8
137.5°	308.7	298.8	285.8	278.0	270.1	251.9	232.5	214.0	197.3	182.2	169.6
140°	292.6	285.1	273.1	266.0	258.8	243.4	227.3	211.6	196.9	183.9	172.3
142.5°	277.9	271.1	260.8	254.8	248.9	236.2	222.5	209.6	196.9	185.3	174.3
145°	263.9	258.1	249.6	244.8	240.0	229.7	218.1	207.2	196.2	185.6	175.7
147.5°	251.9	246.8	240.3	236.4	232.5	223.9	214.3	205.1	195.2	186.0	177.1
150°	241.7	237.2	231.8	228.7	225.6	218.8	210.9	202.7	194.2	186.0	178.1
152.5°	232.5	229.0	224.6	222.2	219.8	213.7	207.2	200.0	192.5	185.3	178.8
155°	224.3	221.5	218.1	216.0	214.0	208.9	203.4	197.3	190.8	184.6	179.1
157.5°	216.7	214.7	211.9	210.2	208.5	204.1	199.3	194.5	189.0	183.9	179.1
160°	209.9	207.8	205.8	204.4	203.1	199.3	195.5	191.4	187.0	182.9	179.1
162.5°	203.4	201.4	200.0	198.8	197.6	194.9	191.8	188.7	184.9	181.9	179.1
165°	197.3	195.9	194.5	193.6	192.8	190.4	188.4	185.6	182.9	180.5	178.4
167.5°	191.4	190.4	189.7	189.2	188.7	186.7	184.9	182.9	180.8	179.1	177.8
170°	186.3	186.0	185.3	184.8	184.3	182.9	181.9	180.2	178.8	177.8	177.1
172.5°	181.9	181.5	181.2	180.8	180.5	179.8	179.1	177.8	176.7	176.4	176.4
175°	178.4	177.8	177.8	177.8	177.8	177.1	176.7	176.1	175.4	175.4	175.7
177.5°	175.7	175.4	175.7	175.6	175.4	175.4	175.0	174.7	174.3	174.3	175.0
180°	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5
2.5°	1958.7	1951.0	1946.4	1944.9	1931.0	1923.4	1918.7	1915.7	1911.0	1898.7	1888.0
5°	2032.6	2011.1	2000.3	1988.0	1966.4	1941.8	1921.8	1909.5	1894.1	1869.5	1846.4
7.5°	2101.8	2069.5	2048.0	2031.1	1994.1	1954.1	1921.8	1895.7	1866.4	1832.6	1800.3
10°	2174.2	2121.8	2094.1	2068.0	2014.1	1961.8	1915.7	1877.2	1835.6	1791.0	1755.6
12.5°	2231.1	2161.8	2131.1	2094.1	2028.0	1966.4	1908.0	1855.6	1801.8	1754.1	1703.3
15°	2297.3	2211.1	2175.7	2128.0	2037.2	1957.2	1881.8	1824.9	1769.5	1698.7	1644.9
17.5°	2335.7	2235.7	2184.9	2143.4	2044.9	1948.0	1860.3	1789.5	1724.9	1654.1	1597.2
20°	2374.2	2260.3	2203.4	2144.9	2028.0	1924.9	1832.6	1747.9	1680.2	1603.3	1544.8
22.5°	2386.5	2254.2	2194.2	2140.3	2017.2	1901.8	1795.6	1709.5	1631.0	1554.1	1487.9
25°	2386.5	2252.6	2181.8	2112.6	1983.4	1864.9	1758.7	1664.9	1577.1	1500.2	1434.1
27.5°	2361.9	2221.9	2148.0	2084.9	1951.0	1823.3	1714.1	1611.0	1526.4	1449.4	1374.0
30°	2331.1	2177.2	2103.4	2028.0	1898.7	1777.2	1658.7	1563.3	1474.1	1386.4	1318.6
32.5°	2292.6	2129.5	2048.0	1971.1	1834.1	1707.9	1598.7	1504.8	1420.2	1329.4	1254.0
35°	2237.2	2058.8	1968.0	1900.3	1767.9	1637.2	1532.5	1440.2	1358.7	1264.8	1183.2
37.5°	2166.5	1994.1	1901.8	1818.7	1681.8	1561.8	1463.3	1374.0	1294.0	1207.9	1117.1
40°	2083.4	1903.3	1823.3	1735.6	1591.0	1477.1	1384.8	1304.8	1224.8	1143.2	1055.5
42.5°	1989.5	1811.0	1721.8	1637.2	1498.7	1386.4	1300.2	1227.9	1154.0	1078.6	984.8
45°	1877.2	1709.5	1623.3	1543.3	1409.4	1294.0	1215.6	1146.3	1083.2	1006.3	923.2
47.5°	1751.0	1604.8	1517.1	1431.0	1300.2	1200.2	1123.2	1064.8	1010.9	934.0	858.6
50°	1627.9	1483.3	1412.5	1324.8	1204.8	1110.9	1032.5	983.2	941.7	866.3	798.6
52.5°	1472.5	1363.3	1295.6	1220.2	1104.8	1009.4	947.8	904.7	855.5	797.0	737.0
55°	1335.6	1234.0	1180.2	1109.4	995.5	910.9	858.6	818.6	780.1	727.8	680.1
57.5°	1180.2	1117.1	1063.2	1001.7	889.4	817.0	770.9	737.0	701.6	658.6	620.1
60°	1017.1	987.8	935.5	886.3	790.9	727.8	689.3	658.6	624.7	589.3	557.0
62.5°	872.4	855.5	824.7	786.3	697.0	643.2	604.7	581.6	557.0	524.7	493.9
65°	735.5	727.8	698.6	670.9	609.3	561.6	527.8	513.9	486.2	461.6	433.9
67.5°	613.9	604.7	587.8	575.5	523.2	478.5	461.6	443.1	420.1	401.6	378.5
70°	490.8	489.3	478.5	463.1	435.4	403.1	386.2	373.9	350.8	337.0	320.0
72.5°	381.6	389.3	380.1	373.9	355.4	332.4	317.0	309.3	290.8	280.0	267.7
75°	284.7	290.8	295.4	284.7	280.0	269.3	255.4	247.7	238.5	223.1	218.5
77.5°	193.9	207.7	207.7	210.8	212.3	206.2	195.4	189.3	178.5	175.4	169.3
80°	127.7	140.0	141.6	144.6	149.3	149.3	141.6	140.0	129.2	127.7	123.1
82.5°	73.9	84.6	90.8	95.4	93.9	100.0	93.9	92.3	86.2	86.2	83.1
85°	40.0	41.5	44.6	47.7	50.8	53.9	53.9	52.3	50.8	49.2	46.2
87.5°	15.4	15.4	16.9	15.4	16.9	20.0	21.5	21.5	20.0	18.5	15.4
90°	4.8	2.7	2.7	2.7	2.4	2.1	1.0	0.3	1.0	2.1	2.4
92.5°	52.0	30.8	26.4	21.9	15.7	10.6	6.8	4.8	6.8	10.6	15.7
95°	72.5	42.7	35.6	28.4	20.2	15.7	12.3	11.3	12.3	15.7	20.2
97.5°	69.1	45.5	39.4	33.2	26.0	21.9	18.8	18.8	18.8	21.9	26.0
100°	70.1	49.9	44.4	39.0	32.5	28.4	26.0	26.0	26.0	28.4	32.5
102.5°	73.5	55.7	50.6	45.5	39.3	35.6	33.5	32.8	33.5	35.6	39.3
105°	79.3	62.9	58.0	53.0	46.8	42.7	41.0	40.0	41.0	42.7	46.8
107.5°	85.5	70.4	65.4	60.5	54.7	50.3	48.5	47.9	48.5	50.3	54.7
110°	92.6	77.6	73.0	68.4	62.2	58.1	56.4	55.7	56.4	58.1	62.2

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	99.5	85.1	80.5	75.9	69.7	66.0	63.9	63.2	63.9	66.0	69.7
115°	106.7	93.0	88.4	83.8	77.3	73.8	71.4	70.4	71.4	73.8	77.3
117.5°	113.5	100.5	95.7	90.9	84.8	81.0	79.0	77.9	79.0	81.0	84.8
120°	120.7	107.7	102.9	98.1	92.3	88.5	86.1	85.5	86.1	88.5	92.3
122.5°	127.5	114.5	109.9	105.3	98.8	95.4	93.0	92.3	93.0	95.4	98.8
125°	133.7	121.4	116.6	111.8	105.3	101.5	99.5	98.1	99.5	101.5	105.3
127.5°	139.5	127.5	122.7	117.9	111.1	107.0	104.6	103.6	104.6	107.0	111.1
130°	145.3	133.7	128.8	123.8	117.3	112.1	109.4	108.0	109.4	112.1	117.3
132.5°	150.1	138.5	133.8	129.2	122.0	117.3	113.5	112.5	113.5	117.3	122.0
135°	154.5	143.2	138.8	134.3	127.2	121.4	117.9	116.6	117.9	121.4	127.2
137.5°	157.9	147.3	143.0	138.8	131.3	125.8	122.0	120.7	122.0	125.8	131.3
140°	161.4	151.1	147.0	142.9	135.7	129.9	126.1	125.1	126.1	129.9	135.7
142.5°	164.4	154.5	150.6	146.7	139.8	134.3	130.9	129.9	130.9	134.3	139.8
145°	166.5	157.6	153.8	150.1	143.6	138.8	135.4	134.3	135.4	138.8	143.6
147.5°	168.9	160.3	156.9	153.5	148.0	142.9	139.8	139.5	139.8	142.9	148.0
150°	170.6	163.1	159.8	156.6	151.4	147.3	144.6	144.3	144.6	147.3	151.4
152.5°	172.0	165.5	162.6	159.6	155.2	151.4	148.7	148.7	148.7	151.4	155.2
155°	173.3	167.5	165.0	162.4	158.6	155.2	153.2	152.8	153.2	155.2	158.6
157.5°	174.3	169.2	167.1	165.1	161.7	159.0	156.9	156.9	156.9	159.0	161.7
160°	175.0	170.9	169.0	167.2	164.4	162.0	160.7	160.7	160.7	162.0	164.4
162.5°	175.7	172.0	170.6	169.2	166.8	164.8	163.7	164.1	163.7	164.8	166.8
165°	175.7	172.6	171.6	170.6	168.9	167.2	166.5	166.5	166.5	167.2	168.9
167.5°	175.7	173.3	172.4	171.6	170.6	169.2	168.9	169.2	168.9	169.2	170.6
170°	175.4	173.7	173.1	172.6	172.0	170.9	170.6	170.9	170.6	170.9	172.0
172.5°	175.0	174.0	173.6	173.3	173.0	172.3	172.3	172.6	172.3	172.3	173.0
175°	174.7	174.0	174.0	174.0	173.7	173.3	173.3	173.7	173.3	173.3	173.7
177.5°	174.3	174.0	174.0	174.0	174.0	173.7	174.0	174.3	174.0	173.7	174.0
180°	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5
2.5°	1878.7	1875.7	1872.6	1860.3	1849.5	1831.0	1815.6	1809.5	1808.0	1809.5	1804.9
5°	1824.9	1823.3	1812.6	1791.0	1771.0	1749.5	1734.1	1718.7	1709.5	1709.5	1698.7
7.5°	1774.1	1763.3	1754.1	1726.4	1703.3	1674.1	1651.0	1637.2	1629.5	1612.5	1612.5
10°	1720.2	1704.9	1692.5	1666.4	1632.5	1603.3	1574.1	1557.1	1543.3	1531.0	1526.4
12.5°	1666.4	1654.1	1631.0	1603.3	1569.5	1532.5	1501.8	1489.4	1457.1	1431.0	1432.5
15°	1615.6	1587.9	1577.1	1537.1	1497.1	1461.7	1417.1	1381.7	1355.6	1338.7	1317.1
17.5°	1558.7	1531.0	1511.0	1477.1	1424.8	1369.4	1326.3	1278.6	1252.5	1223.3	1209.4
20°	1495.6	1472.5	1457.1	1403.3	1340.2	1274.0	1226.3	1197.1	1167.9	1146.3	1134.0
22.5°	1441.7	1412.5	1394.0	1321.7	1252.5	1186.3	1149.4	1124.8	1100.2	1081.7	1075.5
25°	1372.5	1355.6	1311.0	1247.9	1163.2	1118.6	1086.3	1054.0	1040.1	1027.8	1014.0
27.5°	1315.6	1274.0	1243.3	1160.2	1107.9	1057.1	1024.8	1000.1	983.2	970.9	960.1
30°	1244.8	1206.3	1163.2	1094.0	1046.3	998.6	969.4	949.4	930.9	923.2	914.0
32.5°	1170.9	1135.5	1094.0	1038.6	980.1	943.2	920.1	898.6	886.3	878.6	867.8
35°	1104.8	1060.2	1032.5	980.1	932.4	890.9	869.4	850.9	837.0	834.0	832.4
37.5°	1034.0	1000.1	974.0	920.1	880.1	844.7	824.7	804.7	797.0	795.5	789.3
40°	972.4	943.2	918.6	867.8	824.7	792.4	777.0	764.7	757.0	757.0	755.5
42.5°	918.6	887.8	863.2	817.0	778.6	749.3	732.4	720.1	717.0	718.6	717.0
45°	858.6	832.4	807.8	760.1	727.8	706.3	687.8	681.6	677.0	678.6	680.1
47.5°	801.7	780.1	755.5	717.0	680.1	657.0	646.2	640.1	640.1	640.1	643.2
50°	750.9	726.3	704.7	664.7	630.9	612.4	603.2	595.5	597.0	598.5	600.1
52.5°	690.9	669.3	653.9	613.9	589.3	566.2	555.5	557.0	555.5	555.5	558.5
55°	638.6	617.0	601.6	564.7	540.1	524.7	515.5	510.8	512.4	509.3	515.5
57.5°	580.1	561.6	550.8	515.5	493.9	480.1	472.4	464.7	467.8	466.2	464.7
60°	529.3	507.8	490.8	466.2	447.8	430.8	426.2	418.5	421.6	418.5	417.0
62.5°	470.8	453.9	441.6	417.0	401.6	387.7	377.0	372.4	370.8	366.2	361.6
65°	412.4	403.1	390.8	366.2	350.8	340.0	333.9	329.3	327.7	315.4	301.6
67.5°	358.5	352.4	340.0	321.6	307.7	297.0	287.7	280.0	270.8	261.6	253.9
70°	307.7	298.5	290.8	273.9	261.6	250.8	241.6	232.3	227.7	218.5	215.4
72.5°	258.5	249.3	241.6	226.2	215.4	204.6	201.6	190.8	186.2	184.6	184.6
75°	207.7	200.0	195.4	181.6	172.3	164.6	160.0	156.9	153.9	150.8	146.2
77.5°	158.5	153.9	150.8	141.6	133.9	129.2	127.7	116.9	113.9	110.8	107.7
80°	115.4	113.9	110.8	103.1	100.0	89.2	89.2	86.2	84.6	84.6	84.6
82.5°	78.5	75.4	73.9	66.2	64.6	63.1	61.5	60.0	61.5	60.0	61.5
85°	41.5	40.0	38.5	38.5	38.5	38.5	38.5	38.5	38.5	36.9	38.5
87.5°	15.4	15.4	15.4	15.4	13.8	15.4	15.4	13.8	15.4	15.4	15.4
90°	2.7	2.7	2.7	4.8	4.8	5.5	6.2	5.8	6.2	6.5	6.8
92.5°	21.9	26.4	30.8	52.0	85.1	117.3	134.0	111.4	82.4	61.5	48.5
95°	28.4	35.6	42.7	72.5	128.5	210.2	278.6	286.5	253.3	200.3	154.5
97.5°	33.2	39.4	45.5	69.1	117.3	201.4	298.1	359.3	364.8	338.4	300.8
100°	39.0	44.4	49.9	70.1	108.7	178.4	274.9	362.4	412.3	419.1	402.4
102.5°	45.5	50.6	55.7	73.5	106.3	163.1	245.8	336.7	409.9	450.6	460.8
105°	53.0	58.0	62.9	79.3	107.7	155.5	224.3	304.6	382.9	442.0	475.9
107.5°	60.5	65.4	70.4	85.5	111.8	153.5	210.2	278.3	349.7	413.6	460.8
110°	68.4	73.0	77.6	92.6	116.6	154.2	203.7	259.5	320.3	379.5	429.0

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	75.9	80.5	85.1	99.5	121.7	156.2	200.7	248.9	298.8	349.4	395.5
115°	83.8	88.4	93.0	106.7	127.2	159.0	200.0	243.1	285.8	327.8	367.8
117.5°	90.9	95.7	100.5	113.5	132.6	161.7	199.6	240.0	278.3	313.8	346.3
120°	98.1	102.9	107.7	120.7	138.5	164.8	199.6	237.6	273.5	305.3	332.6
122.5°	105.3	109.9	114.5	127.5	143.9	167.9	199.3	234.9	269.4	299.8	324.1
125°	111.8	116.6	121.4	133.7	149.4	170.9	199.0	231.8	264.6	294.0	317.6
127.5°	117.9	122.7	127.5	139.5	154.2	173.3	198.3	227.7	259.1	287.5	311.1
130°	123.8	128.8	133.7	145.3	158.6	176.1	197.9	223.9	252.3	279.3	302.5
132.5°	129.2	133.8	138.5	150.1	163.1	178.4	197.6	220.5	245.1	270.1	292.6
135°	134.3	138.8	143.2	154.5	166.8	180.8	197.3	217.1	238.6	260.8	281.7
137.5°	138.8	143.0	147.3	157.9	169.6	182.2	197.3	214.0	232.5	251.9	270.1
140°	142.9	147.0	151.1	161.4	172.3	183.9	196.9	211.6	227.3	243.4	258.8
142.5°	146.7	150.6	154.5	164.4	174.3	185.3	196.9	209.6	222.5	236.2	248.9
145°	150.1	153.8	157.6	166.5	175.7	185.6	196.2	207.2	218.1	229.7	240.0
147.5°	153.5	156.9	160.3	168.9	177.1	186.0	195.2	205.1	214.3	223.9	232.5
150°	156.6	159.8	163.1	170.6	178.1	186.0	194.2	202.7	210.9	218.8	225.6
152.5°	159.6	162.6	165.5	172.0	178.8	185.3	192.5	200.0	207.2	213.7	219.8
155°	162.4	165.0	167.5	173.3	179.1	184.6	190.8	197.3	203.4	208.9	214.0
157.5°	165.1	167.1	169.2	174.3	179.1	183.9	189.0	194.5	199.3	204.1	208.5
160°	167.2	169.0	170.9	175.0	179.1	182.9	187.0	191.4	195.5	199.3	203.1
162.5°	169.2	170.6	172.0	175.7	179.1	181.9	184.9	188.7	191.8	194.9	197.6
165°	170.6	171.6	172.6	175.7	178.4	180.5	182.9	185.6	188.4	190.4	192.8
167.5°	171.6	172.4	173.3	175.7	177.8	179.1	180.8	182.9	184.9	186.7	188.7
170°	172.6	173.1	173.7	175.4	177.1	177.8	178.8	180.2	181.9	182.9	184.3
172.5°	173.3	173.6	174.0	175.0	176.4	176.4	176.7	177.8	179.1	179.8	180.5
175°	174.0	174.0	174.0	174.7	175.7	175.4	175.4	176.1	176.7	177.1	177.8
177.5°	174.0	174.0	174.0	174.3	175.0	174.3	174.3	174.7	175.0	175.4	175.4
180°	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5
2.5°	1804.9	1811.0	1803.3	1808.0	1797.2	1795.6	1797.2	1797.2	1798.7	1800.3	1801.8
5°	1703.3	1701.8	1692.5	1686.4	1681.8	1686.4	1689.5	1692.5	1689.5	1692.5	1694.1
7.5°	1607.9	1603.3	1598.7	1587.9	1591.0	1587.9	1597.2	1592.5	1592.5	1600.2	1606.4
10°	1523.3	1514.1	1511.0	1498.7	1489.4	1487.9	1498.7	1503.3	1507.9	1511.0	1523.3
12.5°	1414.0	1400.2	1389.4	1394.0	1367.9	1378.7	1381.7	1375.6	1394.0	1415.6	1403.3
15°	1297.1	1298.6	1277.1	1269.4	1247.9	1254.0	1255.6	1271.0	1286.3	1284.8	1303.3
17.5°	1210.9	1201.7	1183.2	1181.7	1172.5	1177.1	1175.6	1187.9	1183.2	1190.9	1206.3
20°	1130.9	1124.8	1109.4	1103.2	1106.3	1103.2	1104.8	1106.3	1110.9	1127.9	1124.8
22.5°	1067.8	1060.2	1060.2	1052.5	1043.2	1040.1	1047.8	1052.5	1058.6	1061.7	1069.4
25°	1012.5	1006.3	998.6	994.0	986.3	987.8	992.4	998.6	1003.2	1009.4	1015.5
27.5°	955.5	955.5	947.8	946.3	943.2	941.7	947.8	950.9	950.9	955.5	961.7
30°	910.9	910.9	903.2	901.7	900.1	900.1	904.7	906.3	907.8	912.4	915.5
32.5°	867.8	866.3	863.2	864.7	863.2	864.7	864.7	866.3	869.4	870.9	877.0
35°	827.8	829.3	826.3	826.3	824.7	826.3	829.3	830.9	832.4	835.5	835.5
37.5°	789.3	792.4	790.9	795.5	795.5	795.5	795.5	798.6	798.6	798.6	797.0
40°	755.5	755.5	754.0	757.0	760.1	760.1	761.6	761.6	763.2	763.2	761.6
42.5°	717.0	720.1	724.7	726.3	729.3	727.8	732.4	730.9	732.4	729.3	726.3
45°	681.6	681.6	687.8	693.9	695.5	695.5	695.5	698.6	695.5	690.9	689.3
47.5°	643.2	646.2	649.3	657.0	658.6	658.6	658.6	658.6	655.5	655.5	655.5
50°	604.7	606.2	607.8	610.9	615.5	613.9	613.9	613.9	620.1	613.9	615.5
52.5°	558.5	560.1	561.6	567.8	566.2	566.2	567.8	567.8	572.4	570.9	567.8
55°	512.4	512.4	515.5	515.5	515.5	518.5	520.1	523.2	521.6	523.2	524.7
57.5°	466.2	463.1	461.6	461.6	466.2	464.7	466.2	466.2	472.4	475.5	477.0
60°	412.4	412.4	410.8	401.6	401.6	400.1	404.7	407.8	410.8	424.7	423.1
62.5°	357.0	350.8	344.7	346.2	337.0	341.6	338.5	341.6	350.8	361.6	363.1
65°	301.6	297.0	290.8	289.3	286.2	290.8	289.3	290.8	295.4	301.6	309.3
67.5°	252.3	250.8	247.7	246.2	246.2	246.2	249.3	249.3	250.8	255.4	260.0
70°	215.4	213.9	215.4	212.3	213.9	212.3	213.9	215.4	217.0	218.5	223.1
72.5°	181.6	181.6	181.6	178.5	181.6	180.0	180.0	181.6	183.1	184.6	187.7
75°	144.6	141.6	138.5	135.4	133.9	136.9	138.5	136.9	141.6	147.7	147.7
77.5°	109.2	107.7	107.7	107.7	109.2	107.7	110.8	109.2	110.8	110.8	113.9
80°	84.6	83.1	84.6	84.6	83.1	86.2	84.6	84.6	86.2	87.7	86.2
82.5°	61.5	63.1	61.5	61.5	61.5	64.6	61.5	61.5	61.5	63.1	63.1
85°	38.5	38.5	38.5	38.5	40.0	38.5	40.0	38.5	41.5	40.0	40.0
87.5°	13.8	15.4	16.9	16.9	16.9	16.9	15.4	16.9	18.5	16.9	18.5
90°	6.8	6.8	7.2	7.5	7.2	7.2	7.2	7.5	7.2	6.8	6.8
92.5°	44.2	40.0	34.9	32.5	31.1	31.1	31.1	32.5	34.9	40.0	44.2
95°	138.0	121.4	104.6	94.0	87.9	83.4	87.9	94.0	104.6	121.4	138.0
97.5°	281.6	262.5	239.3	218.8	208.5	200.3	208.5	218.8	239.3	262.5	281.6
100°	389.8	377.1	347.3	326.5	316.2	313.5	316.2	326.5	347.3	377.1	389.8
102.5°	457.4	454.0	438.6	424.9	414.0	411.9	414.0	424.9	438.6	454.0	457.4
105°	482.9	489.9	490.6	487.8	483.0	481.0	483.0	487.8	490.6	489.9	482.9
107.5°	475.2	489.5	504.6	510.7	513.5	513.8	513.5	510.7	504.6	489.5	475.2
110°	447.8	466.6	490.9	505.3	511.4	514.5	511.4	505.3	490.9	466.6	447.8

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	414.3	433.1	461.5	479.6	488.9	494.3	488.9	479.6	461.5	433.1	414.3
115°	384.2	400.7	427.7	448.2	459.1	461.8	459.1	448.2	427.7	400.7	384.2
117.5°	360.6	375.0	398.9	416.7	428.3	430.1	428.3	416.7	398.9	375.0	360.6
120°	344.8	356.9	376.4	391.4	400.3	404.1	400.3	391.4	376.4	356.9	344.8
122.5°	334.4	344.6	360.3	372.6	379.8	383.6	379.8	372.6	360.3	344.6	334.4
125°	327.0	336.4	350.1	360.0	366.5	368.5	366.5	360.0	350.1	336.4	327.0
127.5°	320.0	328.9	342.5	351.4	356.9	358.9	356.9	351.4	342.5	328.9	320.0
130°	311.6	320.7	334.7	343.2	348.7	350.7	348.7	343.2	334.7	320.7	311.6
132.5°	301.6	310.7	324.4	334.3	339.5	341.5	339.5	334.3	324.4	310.7	301.6
135°	290.2	298.8	312.5	322.0	327.5	329.5	327.5	322.0	312.5	298.8	290.2
137.5°	278.0	285.8	298.8	308.7	313.1	315.5	313.1	308.7	298.8	285.8	278.0
140°	266.0	273.1	285.1	292.6	297.4	300.1	297.4	292.6	285.1	273.1	266.0
142.5°	254.8	260.8	271.1	277.9	282.0	283.7	282.0	277.9	271.1	260.8	254.8
145°	244.8	249.6	258.1	263.9	267.3	269.0	267.3	263.9	258.1	249.6	244.8
147.5°	236.4	240.3	246.8	251.9	254.7	255.4	254.7	251.9	246.8	240.3	236.4
150°	228.7	231.8	237.2	241.7	243.7	244.1	243.7	241.7	237.2	231.8	228.7
152.5°	222.2	224.6	229.0	232.5	233.5	233.8	233.5	232.5	229.0	224.6	222.2
155°	216.0	218.1	221.5	224.3	225.3	225.3	225.3	224.3	221.5	218.1	216.0
157.5°	210.2	211.9	214.7	216.7	217.4	217.4	217.4	216.7	214.7	211.9	210.2
160°	204.4	205.8	207.8	209.9	210.2	210.2	210.2	209.9	207.8	205.8	204.4
162.5°	198.8	200.0	201.4	203.4	203.7	203.4	203.7	203.4	201.4	200.0	198.8
165°	193.6	194.5	195.9	197.3	196.9	196.6	196.9	197.3	195.9	194.5	193.6
167.5°	189.2	189.7	190.4	191.4	191.4	191.1	191.4	191.4	190.4	189.7	189.2
170°	184.8	185.3	186.0	186.3	186.0	186.0	186.0	186.3	186.0	185.3	184.8
172.5°	180.8	181.2	181.5	181.9	181.5	180.8	181.5	181.9	181.5	181.2	180.8
175°	177.8	177.8	177.8	178.4	177.8	177.1	177.8	178.4	177.8	177.8	177.8
177.5°	175.6	175.7	175.4	175.7	175.0	174.3	175.0	175.7	175.4	175.7	175.6
180°	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5	1909.5
2.5°	1808.0	1815.6	1812.6	1801.8	1806.4	1815.6	1824.9	1837.2	1844.9	1851.0	1854.1
5°	1701.8	1715.6	1712.6	1712.6	1718.7	1734.1	1749.5	1775.6	1784.9	1795.6	1811.0
7.5°	1607.9	1618.7	1627.9	1631.0	1640.2	1660.2	1680.2	1709.5	1732.6	1744.9	1754.1
10°	1524.8	1532.5	1546.4	1554.1	1563.3	1587.9	1617.2	1647.9	1671.0	1692.5	1704.9
12.5°	1418.7	1449.4	1467.9	1480.2	1492.5	1529.4	1552.5	1586.4	1614.1	1634.1	1652.5
15°	1300.2	1337.1	1347.9	1395.6	1426.4	1455.6	1491.0	1531.0	1557.1	1580.2	1604.8
17.5°	1200.2	1226.3	1238.6	1289.4	1315.6	1361.7	1412.5	1463.3	1503.3	1520.2	1544.8
20°	1137.1	1150.9	1175.6	1192.5	1220.2	1274.0	1329.4	1391.0	1451.0	1467.9	1492.5
22.5°	1072.5	1090.9	1107.9	1130.9	1152.5	1189.4	1244.8	1312.5	1377.1	1407.9	1437.1
25°	1014.0	1032.5	1043.2	1067.8	1087.8	1124.8	1163.2	1232.5	1309.4	1335.6	1381.7
27.5°	967.8	978.6	997.1	1007.8	1030.9	1064.8	1100.2	1152.5	1227.9	1272.5	1317.1
30°	921.7	929.4	944.8	960.1	977.1	1000.1	1040.1	1090.9	1160.2	1198.6	1243.3
32.5°	875.5	887.8	897.1	907.8	926.3	954.0	981.7	1030.9	1086.3	1129.4	1174.0
35°	837.0	841.7	854.0	866.3	878.6	903.2	932.4	980.1	1029.4	1063.2	1103.2
37.5°	795.5	803.2	812.4	817.0	837.0	852.4	883.2	920.1	978.6	1000.1	1040.1
40°	763.2	761.6	770.9	778.6	787.8	812.4	830.9	870.9	917.1	950.9	975.5
42.5°	723.2	723.2	726.3	735.5	747.8	763.2	784.7	818.6	866.3	890.9	920.1
45°	690.9	686.3	687.8	693.9	701.6	717.0	738.6	767.8	815.5	835.5	866.3
47.5°	652.4	647.8	647.8	653.9	660.1	670.9	687.8	721.6	760.1	786.3	809.3
50°	609.3	610.9	609.3	613.9	617.0	627.8	646.2	673.9	709.3	730.9	757.0
52.5°	569.3	566.2	564.7	567.8	573.9	581.6	601.6	626.2	660.1	681.6	704.7
55°	520.1	523.2	523.2	523.2	532.4	535.5	550.8	575.5	609.3	626.2	647.8
57.5°	475.5	473.9	477.0	475.5	483.1	493.9	506.2	524.7	558.5	575.5	595.5
60°	426.2	427.8	429.3	429.3	435.4	446.2	460.1	477.0	504.7	521.6	540.1
62.5°	366.2	373.9	381.6	384.7	393.9	401.6	410.8	429.3	453.9	466.2	483.1
65°	309.3	320.0	330.8	338.5	344.7	352.4	364.7	381.6	401.6	413.9	430.8
67.5°	260.0	267.7	281.6	289.3	301.6	310.8	318.5	332.4	357.0	361.6	375.4
70°	224.6	227.7	233.9	240.0	253.9	261.6	270.8	284.7	303.1	313.9	321.6
72.5°	189.3	190.8	193.9	200.0	206.2	215.4	226.2	238.5	255.4	260.0	270.8
75°	150.8	160.0	160.0	164.6	169.3	173.9	183.1	195.4	206.2	213.9	220.0
77.5°	112.3	116.9	120.0	127.7	133.9	138.5	144.6	153.9	160.0	166.2	170.8
80°	87.7	89.2	90.8	90.8	93.9	100.0	106.2	112.3	120.0	123.1	127.7
82.5°	64.6	64.6	64.6	67.7	69.2	70.8	70.8	73.9	81.6	84.6	89.2
85°	41.5	41.5	41.5	41.5	43.1	44.6	46.2	47.7	47.7	47.7	50.8
87.5°	16.9	20.0	18.5	20.0	20.0	20.0	20.0	21.5	21.5	23.1	23.1
90°	6.8	6.5	6.2	5.8	6.2	5.5	4.8	4.8	2.7	2.7	2.7
92.5°	48.5	61.5	82.4	111.4	134.0	117.3	85.1	52.0	30.8	26.4	21.9
95°	154.5	200.3	253.3	286.5	278.6	210.2	128.5	72.5	42.7	35.6	28.4
97.5°	300.8	338.4	364.8	359.3	298.1	201.4	117.3	69.1	45.5	39.4	33.2
100°	402.4	419.1	412.3	362.4	274.9	178.4	108.7	70.1	49.9	44.4	39.0
102.5°	460.8	450.6	409.9	336.7	245.8	163.1	106.3	73.5	55.7	50.6	45.5
105°	475.9	442.0	382.9	304.6	224.3	155.5	107.7	79.3	62.9	58.0	53.0
107.5°	460.8	413.6	349.7	278.3	210.2	153.5	111.8	85.5	70.4	65.4	60.5
110°	429.0	379.5	320.3	259.5	203.7	154.2	116.6	92.6	77.6	73.0	68.4

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	395.5	349.4	298.8	248.9	200.7	156.2	121.7	99.5	85.1	80.5	75.9
115°	367.8	327.8	285.8	243.1	200.0	159.0	127.2	106.7	93.0	88.4	83.8
117.5°	346.3	313.8	278.3	240.0	199.6	161.7	132.6	113.5	100.5	95.7	90.9
120°	332.6	305.3	273.5	237.6	199.6	164.8	138.5	120.7	107.7	102.9	98.1
122.5°	324.1	299.8	269.4	234.9	199.3	167.9	143.9	127.5	114.5	109.9	105.3
125°	317.6	294.0	264.6	231.8	199.0	170.9	149.4	133.7	121.4	116.6	111.8
127.5°	311.1	287.5	259.1	227.7	198.3	173.3	154.2	139.5	127.5	122.7	117.9
130°	302.5	279.3	252.3	223.9	197.9	176.1	158.6	145.3	133.7	128.8	123.8
132.5°	292.6	270.1	245.1	220.5	197.6	178.4	163.1	150.1	138.5	133.8	129.2
135°	281.7	260.8	238.6	217.1	197.3	180.8	166.8	154.5	143.2	138.8	134.3
137.5°	270.1	251.9	232.5	214.0	197.3	182.2	169.6	157.9	147.3	143.0	138.8
140°	258.8	243.4	227.3	211.6	196.9	183.9	172.3	161.4	151.1	147.0	142.9
142.5°	248.9	236.2	222.5	209.6	196.9	185.3	174.3	164.4	154.5	150.6	146.7
145°	240.0	229.7	218.1	207.2	196.2	185.6	175.7	166.5	157.6	153.8	150.1
147.5°	232.5	223.9	214.3	205.1	195.2	186.0	177.1	168.9	160.3	156.9	153.5
150°	225.6	218.8	210.9	202.7	194.2	186.0	178.1	170.6	163.1	159.8	156.6
152.5°	219.8	213.7	207.2	200.0	192.5	185.3	178.8	172.0	165.5	162.6	159.6
155°	214.0	208.9	203.4	197.3	190.8	184.6	179.1	173.3	167.5	165.0	162.4
157.5°	208.5	204.1	199.3	194.5	189.0	183.9	179.1	174.3	169.2	167.1	165.1
160°	203.1	199.3	195.5	191.4	187.0	182.9	179.1	175.0	170.9	169.0	167.2
162.5°	197.6	194.9	191.8	188.7	184.9	181.9	179.1	175.7	172.0	170.6	169.2
165°	192.8	190.4	188.4	185.6	182.9	180.5	178.4	175.7	172.6	171.6	170.6
167.5°	188.7	186.7	184.9	182.9	180.8	179.1	177.8	175.7	173.3	172.4	171.6
170°	184.3	182.9	181.9	180.2	178.8	177.8	177.1	175.4	173.7	173.1	172.6
172.5°	180.5	179.8	179.1	177.8	176.7	176.4	176.4	175.0	174.0	173.6	173.3
175°	177.8	177.1	176.7	176.1	175.4	175.4	175.7	174.7	174.0	174.0	174.0
177.5°	175.4	175.4	175.0	174.7	174.3	174.3	175.0	174.3	174.0	174.0	174.0
180°	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0	174.0

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1909.5	1909.5	1909.5	1909.5
2.5°	1866.4	1875.7	1891.0	1912.6
5°	1823.3	1849.5	1874.1	1906.4
7.5°	1784.9	1815.6	1849.5	1895.7
10°	1740.2	1778.7	1821.8	1878.7
12.5°	1687.9	1741.8	1791.0	1852.6
15°	1649.5	1689.5	1752.6	1824.9
17.5°	1595.6	1649.5	1712.6	1794.1
20°	1544.8	1601.8	1672.5	1757.2
22.5°	1491.0	1555.6	1626.4	1717.2
25°	1435.6	1504.8	1575.6	1672.5
27.5°	1384.8	1447.9	1527.9	1626.4
30°	1323.3	1395.6	1472.5	1575.6
32.5°	1263.3	1338.7	1417.1	1520.2
35°	1198.6	1274.0	1360.2	1458.7
37.5°	1135.5	1218.6	1297.1	1392.5
40°	1066.3	1152.5	1234.0	1331.0
42.5°	998.6	1087.8	1169.4	1252.5
45°	935.5	1023.2	1097.1	1175.6
47.5°	875.5	954.0	1029.4	1100.2
50°	817.0	883.2	952.4	1010.9
52.5°	755.5	818.6	874.0	926.3
55°	700.1	749.3	798.6	846.3
57.5°	633.9	683.2	726.3	763.2
60°	578.5	609.3	650.9	689.3
62.5°	515.5	550.8	583.2	607.8
65°	453.9	484.7	509.3	530.8
67.5°	401.6	420.1	438.5	461.6
70°	338.5	353.9	375.4	392.4
72.5°	284.7	297.0	307.7	327.7
75°	230.8	241.6	247.7	266.2
77.5°	178.5	189.3	193.9	204.6
80°	136.9	138.5	144.6	153.9
82.5°	93.9	96.9	98.5	106.2
85°	53.9	61.5	60.0	63.1
87.5°	23.1	24.6	27.7	30.8
90°	2.4	2.1	1.0	0.3
92.5°	15.7	10.6	6.8	4.8
95°	20.2	15.7	12.3	11.3
97.5°	26.0	21.9	18.8	18.8
100°	32.5	28.4	26.0	26.0
102.5°	39.3	35.6	33.5	32.8
105°	46.8	42.7	41.0	40.0
107.5°	54.7	50.3	48.5	47.9
110°	62.2	58.1	56.4	55.7

TEST NUMBER: P1026165

CATALOG NUMBER: S124RDIP-B1195D365UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	69.7	66.0	63.9	63.2
115°	77.3	73.8	71.4	70.4
117.5°	84.8	81.0	79.0	77.9
120°	92.3	88.5	86.1	85.5
122.5°	98.8	95.4	93.0	92.3
125°	105.3	101.5	99.5	98.1
127.5°	111.1	107.0	104.6	103.6
130°	117.3	112.1	109.4	108.0
132.5°	122.0	117.3	113.5	112.5
135°	127.2	121.4	117.9	116.6
137.5°	131.3	125.8	122.0	120.7
140°	135.7	129.9	126.1	125.1
142.5°	139.8	134.3	130.9	129.9
145°	143.6	138.8	135.4	134.3
147.5°	148.0	142.9	139.8	139.5
150°	151.4	147.3	144.6	144.3
152.5°	155.2	151.4	148.7	148.7
155°	158.6	155.2	153.2	152.8
157.5°	161.7	159.0	156.9	156.9
160°	164.4	162.0	160.7	160.7
162.5°	166.8	164.8	163.7	164.1
165°	168.9	167.2	166.5	166.5
167.5°	170.6	169.2	168.9	169.2
170°	172.0	170.9	170.6	170.9
172.5°	173.0	172.3	172.3	172.6
175°	173.7	173.3	173.3	173.7
177.5°	174.0	173.7	174.0	174.3
180°	174.0	174.0	174.0	174.0

(END OF REPORT)