

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026201

Luminaire Tested: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026201
REPORT IS A COMBINATION OF REPORTS P999181 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7785.0 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69
1	102	97	94	90	95	92	88	85	81	78	76	71	69	68	62	61	59
2	93	86	80	75	87	81	76	71	72	68	64	63	60	57	55	53	51
3	85	76	69	63	80	72	65	60	64	59	55	56	52	49	49	47	44
4	78	68	60	54	73	64	57	51	57	51	47	50	46	43	44	41	38
5	72	61	52	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	46	41	62	52	44	39	46	40	36	41	37	33	37	33	30
7	62	49	42	36	58	47	40	35	42	36	32	38	33	29	34	30	27
8	57	45	37	32	54	43	36	31	39	33	29	35	30	26	31	27	24
9	54	41	34	29	50	39	32	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16055	16055	16055	16055
5°	16055	18141	16081	13866
10°	15969	20913	15956	12058
15°	15779	23536	15779	10096
20°	15581	25519	15499	8890
25°	15337	25627	15267	8029
30°	15080	21792	14962	7438
35°	14714	16443	14529	6996
40°	14308	11916	14026	6651
45°	13637	9056	13297	6347
50°	12840	7319	12489	5900
55°	11978	6061	11585	5305
60°	11111	5124	10614	4412
65°	10023	4175	9704	3506
70°	9027	3385	8600	2848
75°	7910	2440	7360	2088
80°	6523	1617	5939	1534
85°	4730	832	3922	832

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 20099 cd/sqm

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.6	2.4
10°-20°	575.7	7.4
20°-30°	901.8	11.6
30°-40°	1001.4	12.9
40°-50°	887.4	11.4
50°-60°	691.6	8.9
60°-70°	452.4	5.8
70°-80°	222.0	2.9
80°-90°	55.6	0.7
90°-100°	279.3	3.6
100°-110°	583.1	7.5
110°-120°	518.3	6.7
120°-130°	436.3	5.6
130°-140°	364.0	4.7
140°-150°	277.9	3.6
150°-160°	195.4	2.5
160°-170°	114.9	1.5
170°-180°	37.4	0.5
0°-30°	1668.2	21.4
0°-40°	2669.6	34.3
0°-60°	4248.6	54.6
0°-90°	4978.5	63.9
90°-120°	1380.6	17.7
90°-150°	2458.8	31.6
90°-180°	2806.0	36.0
0°-180°	7785.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1969	1969	1969	1969	1969	
5°	1966	2275	1969	1739	1966	187
15°	1882	3014	1882	1293	1882	531
25°	1724	3251	1717	1018	1724	795
35°	1504	2002	1485	852	1504	940
45°	1212	1023	1182	717	1212	935
55°	873	611	844	535	873	780
65°	547	357	530	300	547	546
75°	274	165	255	141	274	291
85°	65	40	54	40	65	73
90°	1	16	1	16	1	6
95°	25	185	25	185	25	27
105°	89	1065	89	1065	89	94
115°	156	1023	156	1023	156	155
125°	217	816	217	816	217	194
135°	258	730	258	730	258	200
145°	298	596	298	596	298	187
155°	338	499	338	499	338	156
165°	369	435	369	435	369	104
175°	385	392	385	392	385	37
180°	385	385	385	385	385	

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8
2.5°	1972.0	1989.5	1999.0	2006.9	2022.8	2029.1	2041.8	2045.0	2057.7	2056.1	2051.3
5°	1965.7	1995.8	2018.0	2041.8	2070.4	2086.2	2103.7	2129.1	2141.8	2159.2	2170.3
7.5°	1954.6	1995.8	2032.3	2068.8	2114.8	2140.2	2162.4	2202.1	2235.4	2263.9	2295.7
10°	1937.1	1989.5	2043.4	2092.6	2156.0	2186.2	2219.5	2278.2	2324.2	2363.9	2414.6
12.5°	1910.1	1983.1	2043.4	2110.0	2191.0	2232.2	2276.6	2346.4	2400.4	2465.4	2528.9
15°	1881.6	1962.5	2041.8	2129.1	2221.1	2268.7	2313.1	2406.7	2489.2	2563.8	2633.6
17.5°	1849.9	1938.7	2026.0	2122.7	2233.8	2292.5	2344.8	2457.5	2547.9	2644.7	2714.5
20°	1811.8	1908.6	2008.5	2116.4	2241.7	2306.8	2365.5	2494.0	2593.9	2698.6	2785.9
22.5°	1770.5	1875.2	1984.7	2102.1	2232.2	2303.6	2371.8	2509.8	2625.7	2722.4	2839.8
25°	1724.5	1835.6	1948.2	2072.0	2217.9	2295.7	2365.5	2501.9	2625.7	2752.6	2866.8
27.5°	1676.9	1791.2	1908.6	2038.6	2187.8	2263.9	2343.3	2474.9	2619.3	2757.3	2873.1
30°	1624.6	1735.6	1859.4	1983.1	2141.8	2217.9	2298.8	2441.6	2598.7	2736.7	2862.0
32.5°	1567.5	1681.7	1799.1	1927.6	2083.1	2165.6	2240.1	2402.0	2562.2	2698.6	2816.0
35°	1504.0	1611.9	1722.9	1854.6	2008.5	2083.1	2171.9	2340.1	2501.9	2646.3	2722.4
37.5°	1435.8	1538.9	1642.0	1772.1	1919.7	2010.1	2097.3	2267.1	2438.4	2535.2	2574.9
40°	1372.3	1462.7	1553.2	1678.5	1827.6	1921.2	2010.1	2186.2	2336.9	2411.5	2381.3
42.5°	1291.4	1385.0	1465.9	1581.7	1732.5	1819.7	1910.1	2092.6	2214.7	2244.9	2170.3
45°	1212.1	1289.8	1367.6	1480.2	1638.9	1713.4	1810.2	1979.9	2081.5	2054.5	1945.0
47.5°	1134.3	1197.8	1270.8	1380.3	1523.0	1611.9	1702.3	1849.9	1921.2	1883.2	1730.9
50°	1042.3	1105.8	1181.9	1277.1	1415.2	1500.8	1572.2	1708.7	1762.6	1669.0	1485.0
52.5°	955.1	1010.6	1075.6	1164.5	1296.2	1373.9	1451.6	1569.0	1586.5	1478.6	1285.1
55°	872.6	917.0	985.2	1056.6	1177.2	1259.7	1313.6	1413.6	1408.8	1274.0	1107.4
57.5°	786.9	828.2	874.2	948.7	1063.0	1124.8	1183.5	1270.8	1224.8	1110.5	945.6
60°	710.8	734.5	780.6	851.9	948.7	1002.7	1048.7	1096.3	1056.6	932.9	805.9
62.5°	626.7	653.6	687.0	744.1	829.7	880.5	913.8	934.4	893.2	798.0	682.2
65°	547.3	571.1	606.0	656.8	721.9	759.9	777.4	791.7	769.5	661.6	569.6
67.5°	475.9	491.8	523.5	556.9	626.7	636.2	660.0	666.3	621.9	539.4	466.4
70°	404.6	420.4	434.7	474.4	506.1	523.5	528.3	528.3	483.9	429.9	369.7
72.5°	337.9	347.4	361.7	388.7	406.1	418.8	425.2	417.2	376.0	331.6	287.2
75°	274.5	279.2	291.9	309.4	323.6	318.9	317.3	307.8	277.6	245.9	220.5
77.5°	211.0	214.2	228.5	233.2	233.2	238.0	231.6	222.1	196.7	172.9	161.8
80°	158.6	163.4	165.0	168.2	165.0	165.0	160.2	144.4	131.7	120.6	112.6
82.5°	109.5	112.6	114.2	109.5	112.6	107.9	99.9	88.8	80.9	79.3	76.2
85°	65.0	66.6	65.0	65.0	60.3	58.7	52.4	50.8	47.6	47.6	46.0
87.5°	31.7	30.1	27.0	23.8	23.8	22.2	23.8	20.6	23.8	22.2	20.6
90°	0.8	2.3	4.5	5.3	6.1	6.1	6.1	10.6	10.6	12.1	13.6
92.5°	10.6	15.1	23.5	34.8	48.5	58.3	68.1	115.1	188.5	259.7	296.8
95°	25.0	27.3	34.8	44.7	62.8	78.7	94.6	160.5	284.6	465.6	617.0
97.5°	41.6	41.6	48.5	57.5	73.4	87.1	100.7	152.9	259.7	445.9	660.1
100°	57.5	57.5	62.8	71.9	86.3	98.4	110.5	155.2	240.7	395.2	608.7
102.5°	72.7	74.2	78.7	87.1	100.7	112.0	123.4	162.8	235.4	361.1	544.3
105°	88.6	90.8	94.6	103.7	117.3	128.3	139.3	175.6	238.5	344.5	496.6
107.5°	106.0	107.5	111.3	121.1	134.0	145.0	156.0	189.3	247.6	339.9	465.6
110°	123.4	124.9	128.7	137.8	151.4	161.6	171.8	205.2	258.2	341.4	451.2

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	140.1	141.6	146.1	154.4	168.1	178.3	188.5	220.3	269.5	346.0	444.4
115°	156.0	158.2	163.5	171.1	185.5	195.7	205.9	236.2	281.6	352.0	442.9
117.5°	172.6	174.9	179.4	187.7	201.4	212.0	222.6	251.3	293.7	358.1	442.1
120°	189.3	190.8	196.1	204.4	217.3	227.9	238.5	267.2	306.6	364.9	442.1
122.5°	204.4	205.9	211.2	218.8	233.2	243.4	253.6	282.4	318.7	371.7	441.4
125°	217.3	220.3	224.8	233.2	247.6	258.2	268.7	296.0	330.8	378.5	440.6
127.5°	229.4	231.7	237.0	246.0	261.2	271.8	282.4	308.9	341.4	383.8	439.1
130°	239.2	242.3	248.3	259.7	274.0	285.0	296.0	321.7	351.3	389.9	438.3
132.5°	249.1	251.3	259.7	270.3	286.2	296.4	306.6	332.3	361.1	395.2	437.6
135°	258.2	261.2	268.7	281.6	297.5	307.4	317.2	342.2	369.4	400.5	436.8
137.5°	267.2	270.3	278.6	290.7	307.4	316.8	326.3	349.8	375.5	403.5	436.8
140°	277.1	279.3	287.7	300.5	316.4	325.5	334.6	357.3	381.5	407.3	436.1
142.5°	287.7	289.9	297.5	309.6	324.8	333.5	342.2	364.1	386.1	410.3	436.1
145°	297.5	299.8	307.4	318.0	332.3	340.6	349.0	368.7	389.1	411.1	434.5
147.5°	308.9	309.6	316.4	327.8	339.9	347.5	355.1	374.0	392.1	411.8	432.3
150°	319.5	320.2	326.3	335.4	346.7	353.9	361.1	377.8	394.4	411.8	430.0
152.5°	329.3	329.3	335.4	343.7	353.5	360.0	366.4	380.8	395.9	410.3	426.2
155°	338.4	339.2	343.7	351.3	359.6	365.3	371.0	383.8	396.7	408.8	422.4
157.5°	347.5	347.5	352.0	358.1	365.7	370.2	374.7	386.1	396.7	407.3	418.6
160°	355.8	355.8	358.8	364.1	370.2	374.4	378.5	387.6	396.7	405.0	414.1
162.5°	363.4	362.6	364.9	369.4	374.7	377.8	380.8	389.1	396.7	402.7	409.6
165°	368.7	368.7	370.2	374.0	377.8	380.0	382.3	389.1	395.2	399.7	405.0
167.5°	374.7	374.0	374.7	377.8	380.0	381.9	383.8	389.1	393.7	396.7	400.5
170°	378.5	377.8	378.5	380.8	382.3	383.5	384.6	388.4	392.1	393.7	395.9
172.5°	382.3	381.5	381.5	383.1	383.8	384.6	385.3	387.6	390.6	390.6	391.4
175°	384.6	383.8	383.8	384.6	385.3	385.3	385.3	386.8	389.1	388.4	388.4
177.5°	386.1	385.3	384.6	385.3	385.3	385.3	385.3	386.1	387.6	386.1	386.1
180°	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8
2.5°	2064.0	2081.5	2083.1	2098.9	2094.2	2086.2	2100.5	2091.0	2110.0	2103.7	2111.6
5°	2184.6	2208.4	2229.0	2241.7	2263.9	2259.2	2283.0	2275.0	2292.5	2275.0	2297.2
7.5°	2325.8	2365.5	2386.1	2419.4	2428.9	2430.5	2459.1	2465.4	2476.5	2465.4	2478.1
10°	2463.8	2511.4	2559.0	2586.0	2603.4	2627.2	2652.6	2663.7	2671.7	2660.6	2668.5
12.5°	2589.2	2663.7	2716.1	2770.0	2782.7	2803.3	2830.3	2827.1	2858.9	2852.5	2866.8
15°	2705.0	2787.5	2850.9	2893.8	2928.7	2946.1	2996.9	3000.1	2998.5	3014.3	3004.8
17.5°	2808.1	2877.9	2968.3	3023.9	3066.7	3066.7	3095.3	3154.0	3149.2	3147.6	3157.1
20°	2892.2	2971.5	3055.6	3149.2	3184.1	3190.4	3230.1	3260.2	3265.0	3265.0	3265.0
22.5°	2955.6	3049.2	3139.7	3206.3	3233.3	3255.5	3290.4	3309.4	3315.8	3312.6	3315.8
25°	2987.4	3076.2	3168.2	3228.5	3244.4	3257.1	3260.2	3271.4	3269.8	3250.7	3261.8
27.5°	2993.7	3079.4	3139.7	3155.5	3147.6	3139.7	3088.9	3093.7	3079.4	3050.8	3061.9
30°	2965.2	3011.2	3009.6	2960.4	2946.1	2912.8	2866.8	2798.6	2743.1	2719.3	2727.2
32.5°	2862.0	2862.0	2804.9	2693.9	2644.7	2584.4	2501.9	2440.0	2367.1	2351.2	2381.3
35°	2719.3	2638.3	2533.6	2387.7	2313.1	2268.7	2125.9	2081.5	2019.6	2002.2	2016.4
37.5°	2497.1	2362.3	2210.0	2073.6	2010.1	1930.8	1805.4	1742.0	1697.6	1667.4	1681.7
40°	2248.1	2084.7	1926.0	1757.8	1688.0	1623.0	1529.4	1472.3	1400.9	1404.0	1408.8
42.5°	2010.1	1818.1	1640.4	1485.0	1418.3	1364.4	1299.3	1229.5	1204.2	1196.2	1188.3
45°	1757.8	1553.2	1386.6	1270.8	1210.5	1159.7	1099.4	1059.8	1029.6	1023.3	1031.2
47.5°	1519.9	1346.9	1188.3	1080.4	1031.2	1005.8	958.2	921.8	902.7	886.9	896.4
50°	1304.1	1142.3	1015.4	924.9	890.0	872.6	828.2	809.1	790.1	785.3	783.7
52.5°	1126.4	988.4	878.9	805.9	779.0	769.5	736.1	709.2	693.3	698.1	701.2
55°	964.6	847.2	761.5	702.8	680.6	669.5	645.7	626.7	615.6	610.8	614.0
57.5°	821.8	720.3	658.4	610.8	593.3	588.6	563.2	556.9	548.9	544.2	544.2
60°	691.7	620.3	563.2	536.2	517.2	512.4	493.4	485.5	483.9	479.1	475.9
62.5°	582.2	523.5	483.9	455.3	447.4	445.8	433.1	423.6	418.8	415.7	415.7
65°	487.1	444.2	410.9	390.3	383.9	380.8	366.5	363.3	360.1	357.0	355.4
67.5°	406.1	368.1	344.3	330.0	322.1	323.6	315.7	309.4	309.4	307.8	306.2
70°	328.4	304.6	284.0	276.1	272.9	269.7	266.5	261.8	260.2	260.2	260.2
72.5°	258.6	242.7	231.6	226.9	223.7	220.5	217.3	217.3	217.3	215.8	215.8
75°	198.3	192.0	184.0	179.3	179.3	182.4	177.7	172.9	168.2	165.0	166.6
77.5°	149.1	146.0	141.2	133.3	134.9	131.7	131.7	128.5	130.1	130.1	126.9
80°	109.5	104.7	103.1	98.4	99.9	98.4	96.8	96.8	93.6	93.6	93.6
82.5°	76.2	71.4	71.4	69.8	68.2	68.2	66.6	66.6	68.2	65.0	65.0
85°	46.0	44.4	44.4	41.2	41.2	41.2	41.2	42.8	41.2	39.7	39.7
87.5°	20.6	22.2	20.6	19.0	19.0	19.0	17.5	17.5	15.9	17.5	17.5
90°	12.9	13.6	14.4	15.1	15.1	15.1	15.9	16.7	15.9	15.9	15.9
92.5°	246.8	182.4	136.3	107.5	98.0	88.6	77.2	71.9	68.9	68.9	68.9
95°	634.4	561.0	443.6	342.2	305.4	268.7	231.7	208.2	194.6	184.7	194.6
97.5°	795.7	807.8	749.5	666.2	623.8	581.4	529.9	484.5	461.8	443.6	461.8
100°	802.5	913.0	928.1	891.0	863.0	835.0	769.2	723.0	700.3	694.2	700.3
102.5°	745.7	907.7	997.8	1020.5	1013.0	1005.4	971.3	941.0	916.8	912.2	916.8
105°	674.5	847.9	978.9	1053.8	1069.3	1084.8	1086.4	1080.3	1069.7	1065.2	1069.7
107.5°	616.2	774.5	916.0	1020.5	1052.3	1084.1	1117.4	1131.0	1137.1	1137.8	1137.1
110°	574.6	709.3	840.3	950.1	991.8	1033.4	1087.1	1118.9	1132.5	1139.3	1132.5

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	551.1	661.7	773.7	875.9	917.6	959.2	1022.0	1062.1	1082.6	1094.7	1082.6
115°	538.3	632.9	726.0	814.6	851.0	887.3	947.1	992.5	1016.7	1022.8	1016.7
117.5°	531.4	616.2	695.0	766.9	798.7	830.5	883.5	922.8	948.6	952.4	948.6
120°	526.1	605.6	676.0	736.6	763.5	790.4	833.5	866.8	886.5	894.8	886.5
122.5°	520.1	596.5	663.9	717.7	740.4	763.1	797.9	825.2	841.1	849.4	841.1
125°	513.3	585.9	651.1	703.3	724.1	744.9	775.2	797.2	811.5	816.1	811.5
127.5°	504.2	573.8	636.7	688.9	708.6	728.3	758.6	778.2	790.4	794.9	790.4
130°	495.9	558.7	618.5	670.0	690.0	710.1	741.1	760.1	772.2	776.7	772.2
132.5°	488.3	542.8	598.1	648.0	668.1	688.2	718.4	740.4	751.7	756.3	751.7
135°	480.7	528.4	577.6	623.8	642.8	661.7	691.9	713.1	725.2	729.8	725.2
137.5°	473.9	514.8	557.9	598.1	615.5	632.9	661.7	683.6	693.4	698.7	693.4
140°	468.6	503.4	539.0	573.1	589.0	604.9	631.4	648.0	658.6	664.7	658.6
142.5°	464.1	492.8	523.1	551.1	564.4	577.6	600.3	615.5	624.6	628.3	624.6
145°	458.8	483.0	508.7	531.4	542.0	552.6	571.6	584.4	592.0	595.8	592.0
147.5°	454.2	474.7	495.9	514.8	523.5	532.2	546.6	557.9	564.0	565.5	564.0
150°	448.9	467.1	484.5	499.6	506.4	513.3	525.4	535.2	539.8	540.5	539.8
152.5°	442.9	458.8	473.2	486.8	492.1	497.4	507.2	514.8	517.1	517.8	517.1
155°	436.8	450.4	462.6	473.9	478.4	483.0	490.6	496.6	498.9	498.9	498.9
157.5°	430.8	441.4	452.0	461.8	465.6	469.4	475.4	480.0	481.5	481.5	481.5
160°	423.9	433.0	441.4	449.7	452.7	455.7	460.3	464.8	465.6	465.6	465.6
162.5°	417.9	424.7	431.5	437.6	440.2	442.9	445.9	450.4	451.2	450.4	451.2
165°	411.1	417.1	421.7	427.0	428.9	430.8	433.8	436.8	436.1	435.3	436.1
167.5°	405.0	409.6	413.3	417.9	419.0	420.2	421.7	423.9	423.9	423.2	423.9
170°	399.0	402.7	405.0	408.0	409.2	410.3	411.8	412.6	411.8	411.8	411.8
172.5°	393.7	396.7	398.2	399.7	400.4	401.2	402.0	402.7	402.0	400.5	402.0
175°	389.9	391.4	392.1	393.7	393.7	393.7	393.7	395.2	393.7	392.1	393.7
177.5°	386.8	387.6	388.4	388.4	388.8	389.1	388.4	389.1	387.6	386.1	387.6
180°	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8
2.5°	2116.4	2105.3	2103.7	2103.7	2086.2	2095.8	2076.7	2056.1	2046.6	2046.6	2029.1
5°	2292.5	2281.4	2270.3	2252.8	2252.8	2243.3	2213.2	2183.0	2160.8	2141.8	2121.1
7.5°	2473.3	2462.2	2430.5	2413.1	2422.6	2403.5	2363.9	2313.1	2275.0	2244.9	2202.1
10°	2670.1	2639.9	2624.1	2614.5	2581.2	2560.6	2514.6	2440.0	2392.4	2352.8	2297.2
12.5°	2830.3	2839.8	2779.5	2784.3	2751.0	2722.4	2651.0	2579.6	2508.2	2452.7	2370.2
15°	3003.2	2974.7	2938.2	2909.6	2898.5	2863.6	2803.3	2708.1	2630.4	2543.2	2449.5
17.5°	3139.7	3117.5	3082.6	3055.6	3031.8	2947.7	2896.9	2812.9	2706.6	2620.9	2506.7
20°	3255.5	3234.9	3185.7	3168.2	3125.4	3065.1	2992.1	2862.0	2766.8	2673.2	2562.2
22.5°	3304.7	3284.0	3241.2	3219.0	3192.0	3133.3	3063.5	2939.8	2822.4	2705.0	2587.6
25°	3263.4	3263.4	3242.8	3234.9	3211.1	3158.7	3087.3	2982.6	2857.3	2730.4	2590.7
27.5°	3063.5	3103.2	3117.5	3125.4	3125.4	3127.0	3077.8	2976.3	2854.1	2730.4	2584.4
30°	2774.8	2841.4	2900.1	2917.6	2947.7	2981.0	3001.7	2952.5	2843.0	2712.9	2567.0
32.5°	2411.5	2497.1	2606.6	2633.6	2674.8	2774.8	2830.3	2850.9	2790.6	2676.4	2520.9
35°	2049.8	2157.6	2224.3	2306.8	2344.8	2492.4	2616.1	2690.7	2676.4	2608.2	2467.0
37.5°	1734.0	1795.9	1876.8	1964.1	2040.2	2181.4	2335.3	2479.7	2538.4	2505.1	2398.8
40°	1431.0	1504.0	1600.8	1672.2	1724.5	1865.7	2056.1	2213.2	2341.7	2362.3	2297.2
42.5°	1216.8	1289.8	1348.5	1426.3	1467.5	1603.9	1772.1	1968.8	2121.1	2202.1	2173.5
45°	1051.8	1096.3	1143.9	1188.3	1239.1	1359.6	1515.1	1730.9	1902.2	2016.4	2027.5
47.5°	907.5	947.1	988.4	1029.6	1058.2	1151.8	1294.6	1470.7	1657.9	1815.0	1876.8
50°	805.9	825.0	855.1	878.9	912.2	993.1	1107.4	1259.7	1458.0	1627.7	1708.7
52.5°	706.0	729.8	753.6	774.2	796.4	853.5	958.2	1089.9	1261.3	1435.8	1535.7
55°	621.9	640.9	663.2	677.4	690.1	740.9	820.2	921.8	1069.3	1234.3	1358.0
57.5°	553.7	561.6	580.7	588.6	602.9	644.1	701.2	791.7	910.6	1070.9	1172.4
60°	479.1	495.0	509.3	515.6	526.7	555.3	594.9	679.0	782.1	899.5	1015.4
62.5°	418.8	425.2	436.3	444.2	452.2	482.3	515.6	579.1	656.8	755.2	861.5
65°	363.3	366.5	372.8	383.9	388.7	410.9	429.9	475.9	548.9	623.5	729.8
67.5°	306.2	309.4	317.3	323.6	328.4	342.7	363.3	396.6	436.3	518.8	577.5
70°	261.8	261.8	266.5	269.7	274.5	280.8	291.9	317.3	353.8	406.1	460.1
72.5°	218.9	218.9	218.9	223.7	223.7	228.5	234.8	252.3	277.6	318.9	353.8
75°	169.8	171.3	174.5	174.5	176.1	182.4	187.2	192.0	204.7	231.6	263.4
77.5°	128.5	131.7	133.3	130.1	133.3	133.3	139.6	146.0	152.3	160.2	184.0
80°	95.2	96.8	93.6	95.2	95.2	98.4	101.5	99.9	103.1	112.6	119.0
82.5°	63.5	65.0	65.0	65.0	65.0	69.8	69.8	68.2	69.8	71.4	73.0
85°	39.7	38.1	38.1	39.7	38.1	38.1	39.7	41.2	39.7	41.2	42.8
87.5°	17.5	17.5	17.5	17.5	15.9	15.9	17.5	15.9	17.5	15.9	14.3
90°	16.7	15.9	15.1	15.1	15.1	14.4	13.6	12.9	13.6	12.1	10.6
92.5°	71.9	77.2	88.6	98.0	107.5	136.3	182.4	246.8	296.8	259.7	188.5
95°	208.2	231.7	268.7	305.4	342.2	443.6	561.0	634.4	617.0	465.6	284.6
97.5°	484.5	529.9	581.4	623.8	666.2	749.5	807.8	795.7	660.1	445.9	259.7
100°	723.0	769.2	835.0	863.0	891.0	928.1	913.0	802.5	608.7	395.2	240.7
102.5°	941.0	971.3	1005.4	1013.0	1020.5	997.8	907.7	745.7	544.3	361.1	235.4
105°	1080.3	1086.4	1084.8	1069.3	1053.8	978.9	847.9	674.5	496.6	344.5	238.5
107.5°	1131.0	1117.4	1084.1	1052.3	1020.5	916.0	774.5	616.2	465.6	339.9	247.6
110°	1118.9	1087.1	1033.4	991.8	950.1	840.3	709.3	574.6	451.2	341.4	258.2

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1062.1	1022.0	959.2	917.6	875.9	773.7	661.7	551.1	444.4	346.0	269.5
115°	992.5	947.1	887.3	851.0	814.6	726.0	632.9	538.3	442.9	352.0	281.6
117.5°	922.8	883.5	830.5	798.7	766.9	695.0	616.2	531.4	442.1	358.1	293.7
120°	866.8	833.5	790.4	763.5	736.6	676.0	605.6	526.1	442.1	364.9	306.6
122.5°	825.2	797.9	763.1	740.4	717.7	663.9	596.5	520.1	441.4	371.7	318.7
125°	797.2	775.2	744.9	724.1	703.3	651.1	585.9	513.3	440.6	378.5	330.8
127.5°	778.2	758.6	728.3	708.6	688.9	636.7	573.8	504.2	439.1	383.8	341.4
130°	760.1	741.1	710.1	690.0	670.0	618.5	558.7	495.9	438.3	389.9	351.3
132.5°	740.4	718.4	688.2	668.1	648.0	598.1	542.8	488.3	437.6	395.2	361.1
135°	713.1	691.9	661.7	642.8	623.8	577.6	528.4	480.7	436.8	400.5	369.4
137.5°	683.6	661.7	632.9	615.5	598.1	557.9	514.8	473.9	436.8	403.5	375.5
140°	648.0	631.4	604.9	589.0	573.1	539.0	503.4	468.6	436.1	407.3	381.5
142.5°	615.5	600.3	577.6	564.4	551.1	523.1	492.8	464.1	436.1	410.3	386.1
145°	584.4	571.6	552.6	542.0	531.4	508.7	483.0	458.8	434.5	411.1	389.1
147.5°	557.9	546.6	532.2	523.5	514.8	495.9	474.7	454.2	432.3	411.8	392.1
150°	535.2	525.4	513.3	506.4	499.6	484.5	467.1	448.9	430.0	411.8	394.4
152.5°	514.8	507.2	497.4	492.1	486.8	473.2	458.8	442.9	426.2	410.3	395.9
155°	496.6	490.6	483.0	478.4	473.9	462.6	450.4	436.8	422.4	408.8	396.7
157.5°	480.0	475.4	469.4	465.6	461.8	452.0	441.4	430.8	418.6	407.3	396.7
160°	464.8	460.3	455.7	452.7	449.7	441.4	433.0	423.9	414.1	405.0	396.7
162.5°	450.4	445.9	442.9	440.2	437.6	431.5	424.7	417.9	409.6	402.7	396.7
165°	436.8	433.8	430.8	428.9	427.0	421.7	417.1	411.1	405.0	399.7	395.2
167.5°	423.9	421.7	420.2	419.0	417.9	413.3	409.6	405.0	400.5	396.7	393.7
170°	412.6	411.8	410.3	409.2	408.0	405.0	402.7	399.0	395.9	393.7	392.1
172.5°	402.7	402.0	401.2	400.4	399.7	398.2	396.7	393.7	391.4	390.6	390.6
175°	395.2	393.7	393.7	393.7	393.7	392.1	391.4	389.9	388.4	388.4	389.1
177.5°	389.1	388.4	389.1	388.8	388.4	388.4	387.6	386.8	386.1	386.1	387.6
180°	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8
2.5°	2019.6	2011.7	2006.9	2005.3	1991.1	1983.1	1978.4	1975.2	1970.4	1957.7	1946.6
5°	2095.8	2073.6	2062.4	2049.8	2027.5	2002.2	1981.5	1968.8	1953.0	1927.6	1903.8
7.5°	2167.2	2133.8	2111.6	2094.2	2056.1	2014.8	1981.5	1954.6	1924.4	1889.5	1856.2
10°	2241.7	2187.8	2159.2	2132.3	2076.7	2022.8	1975.2	1935.5	1892.7	1846.7	1810.2
12.5°	2300.4	2229.0	2197.3	2159.2	2091.0	2027.5	1967.3	1913.3	1857.8	1808.6	1756.3
15°	2368.6	2279.8	2243.3	2194.1	2100.5	2018.0	1940.3	1881.6	1824.5	1751.5	1696.0
17.5°	2408.3	2305.2	2252.8	2210.0	2108.5	2008.5	1918.1	1845.1	1778.5	1705.5	1646.8
20°	2448.0	2330.6	2271.9	2211.6	2091.0	1984.7	1889.5	1802.3	1732.5	1653.1	1592.8
22.5°	2460.7	2324.2	2262.3	2206.8	2079.9	1960.9	1851.4	1762.6	1681.7	1602.4	1534.1
25°	2460.7	2322.6	2249.7	2178.3	2045.0	1922.8	1813.4	1716.6	1626.2	1546.8	1478.6
27.5°	2435.3	2290.9	2214.7	2149.7	2011.7	1880.0	1767.4	1661.1	1573.8	1494.5	1416.7
30°	2403.5	2244.9	2168.7	2091.0	1957.7	1832.4	1710.2	1611.9	1519.9	1429.4	1359.6
32.5°	2363.9	2195.7	2111.6	2032.3	1891.1	1761.0	1648.4	1551.6	1464.3	1370.7	1293.0
35°	2306.8	2122.7	2029.1	1959.3	1822.9	1688.0	1580.1	1485.0	1400.9	1304.1	1220.0
37.5°	2233.8	2056.1	1960.9	1875.2	1734.0	1610.3	1508.8	1416.7	1334.2	1245.4	1151.8
40°	2148.1	1962.5	1880.0	1789.6	1640.4	1523.0	1427.8	1345.3	1262.9	1178.8	1088.3
42.5°	2051.3	1867.3	1775.3	1688.0	1545.2	1429.4	1340.6	1266.0	1189.9	1112.1	1015.4
45°	1935.5	1762.6	1673.8	1591.3	1453.2	1334.2	1253.3	1181.9	1116.9	1037.6	951.9
47.5°	1805.4	1654.7	1564.3	1475.4	1340.6	1237.5	1158.1	1097.9	1042.3	963.0	885.3
50°	1678.5	1529.4	1456.4	1366.0	1242.2	1145.5	1064.5	1013.8	970.9	893.2	823.4
52.5°	1518.3	1405.6	1335.8	1258.1	1139.1	1040.7	977.3	932.9	882.1	821.8	759.9
55°	1377.1	1272.4	1216.8	1143.9	1026.5	939.2	885.3	844.0	804.4	750.4	701.2
57.5°	1216.8	1151.8	1096.3	1032.8	917.0	842.4	794.8	759.9	723.4	679.0	639.4
60°	1048.7	1018.5	964.6	913.8	815.5	750.4	710.8	679.0	644.1	607.6	574.3
62.5°	899.5	882.1	850.4	810.7	718.7	663.2	623.5	599.7	574.3	541.0	509.3
65°	758.3	750.4	720.3	691.7	628.3	579.1	544.2	529.9	501.3	475.9	447.4
67.5°	633.0	623.5	606.0	593.3	539.4	493.4	475.9	456.9	433.1	414.1	390.3
70°	506.1	504.5	493.4	477.5	449.0	415.7	398.2	385.5	361.7	347.4	330.0
72.5°	393.5	401.4	391.9	385.5	366.5	342.7	326.8	318.9	299.8	288.7	276.1
75°	293.5	299.8	304.6	293.5	288.7	277.6	263.4	255.4	245.9	230.0	225.3
77.5°	199.9	214.2	214.2	217.3	218.9	212.6	201.5	195.1	184.0	180.9	174.5
80°	131.7	144.4	146.0	149.1	153.9	153.9	146.0	144.4	133.3	131.7	126.9
82.5°	76.2	87.3	93.6	98.4	96.8	103.1	96.8	95.2	88.8	88.8	85.7
85°	41.2	42.8	46.0	49.2	52.4	55.5	55.5	53.9	52.4	50.8	47.6
87.5°	15.9	15.9	17.5	15.9	17.5	20.6	22.2	22.2	20.6	19.0	15.9
90°	10.6	6.1	6.1	6.1	5.3	4.5	2.3	0.8	2.3	4.5	5.3
92.5°	115.1	68.1	58.3	48.5	34.8	23.5	15.1	10.6	15.1	23.5	34.8
95°	160.5	94.6	78.7	62.8	44.7	34.8	27.3	25.0	27.3	34.8	44.7
97.5°	152.9	100.7	87.1	73.4	57.5	48.5	41.6	41.6	41.6	48.5	57.5
100°	155.2	110.5	98.4	86.3	71.9	62.8	57.5	57.5	57.5	62.8	71.9
102.5°	162.8	123.4	112.0	100.7	87.1	78.7	74.2	72.7	74.2	78.7	87.1
105°	175.6	139.3	128.3	117.3	103.7	94.6	90.8	88.6	90.8	94.6	103.7
107.5°	189.3	156.0	145.0	134.0	121.1	111.3	107.5	106.0	107.5	111.3	121.1
110°	205.2	171.8	161.6	151.4	137.8	128.7	124.9	123.4	124.9	128.7	137.8

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	220.3	188.5	178.3	168.1	154.4	146.1	141.6	140.1	141.6	146.1	154.4
115°	236.2	205.9	195.7	185.5	171.1	163.5	158.2	156.0	158.2	163.5	171.1
117.5°	251.3	222.6	212.0	201.4	187.7	179.4	174.9	172.6	174.9	179.4	187.7
120°	267.2	238.5	227.9	217.3	204.4	196.1	190.8	189.3	190.8	196.1	204.4
122.5°	282.4	253.6	243.4	233.2	218.8	211.2	205.9	204.4	205.9	211.2	218.8
125°	296.0	268.7	258.2	247.6	233.2	224.8	220.3	217.3	220.3	224.8	233.2
127.5°	308.9	282.4	271.8	261.2	246.0	237.0	231.7	229.4	231.7	237.0	246.0
130°	321.7	296.0	285.0	274.0	259.7	248.3	242.3	239.2	242.3	248.3	259.7
132.5°	332.3	306.6	296.4	286.2	270.3	259.7	251.3	249.1	251.3	259.7	270.3
135°	342.2	317.2	307.4	297.5	281.6	268.7	261.2	258.2	261.2	268.7	281.6
137.5°	349.8	326.3	316.8	307.4	290.7	278.6	270.3	267.2	270.3	278.6	290.7
140°	357.3	334.6	325.5	316.4	300.5	287.7	279.3	277.1	279.3	287.7	300.5
142.5°	364.1	342.2	333.5	324.8	309.6	297.5	289.9	287.7	289.9	297.5	309.6
145°	368.7	349.0	340.6	332.3	318.0	307.4	299.8	297.5	299.8	307.4	318.0
147.5°	374.0	355.1	347.5	339.9	327.8	316.4	309.6	308.9	309.6	316.4	327.8
150°	377.8	361.1	353.9	346.7	335.4	326.3	320.2	319.5	320.2	326.3	335.4
152.5°	380.8	366.4	360.0	353.5	343.7	335.4	329.3	329.3	329.3	335.4	343.7
155°	383.8	371.0	365.3	359.6	351.3	343.7	339.2	338.4	339.2	343.7	351.3
157.5°	386.1	374.7	370.2	365.7	358.1	352.0	347.5	347.5	347.5	352.0	358.1
160°	387.6	378.5	374.4	370.2	364.1	358.8	355.8	355.8	355.8	358.8	364.1
162.5°	389.1	380.8	377.8	374.7	369.4	364.9	362.6	363.4	362.6	364.9	369.4
165°	389.1	382.3	380.0	377.8	374.0	370.2	368.7	368.7	368.7	370.2	374.0
167.5°	389.1	383.8	381.9	380.0	377.8	374.7	374.0	374.7	374.0	374.7	377.8
170°	388.4	384.6	383.5	382.3	380.8	378.5	377.8	378.5	377.8	378.5	380.8
172.5°	387.6	385.3	384.6	383.8	383.1	381.5	381.5	382.3	381.5	381.5	383.1
175°	386.8	385.3	385.3	385.3	384.6	383.8	383.8	384.6	383.8	383.8	384.6
177.5°	386.1	385.3	385.3	385.3	385.3	384.6	385.3	386.1	385.3	384.6	385.3
180°	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8
2.5°	1937.1	1933.9	1930.8	1918.1	1907.0	1887.9	1872.1	1865.7	1864.1	1865.7	1861.0
5°	1881.6	1880.0	1868.9	1846.7	1826.1	1803.8	1788.0	1772.1	1762.6	1762.6	1751.5
7.5°	1829.2	1818.1	1808.6	1780.0	1756.3	1726.1	1702.3	1688.0	1680.1	1662.6	1662.6
10°	1773.7	1757.8	1745.1	1718.2	1683.3	1653.1	1623.0	1605.5	1591.3	1578.6	1573.8
12.5°	1718.2	1705.5	1681.7	1653.1	1618.2	1580.1	1548.4	1535.7	1502.4	1475.4	1477.0
15°	1665.8	1637.3	1626.2	1584.9	1543.7	1507.2	1461.2	1424.7	1397.7	1380.3	1358.0
17.5°	1607.1	1578.6	1557.9	1523.0	1469.1	1412.0	1367.6	1318.4	1291.4	1261.3	1247.0
20°	1542.1	1518.3	1502.4	1446.9	1381.8	1313.6	1264.4	1234.3	1204.2	1181.9	1169.2
22.5°	1486.5	1456.4	1437.4	1362.8	1291.4	1223.2	1185.1	1159.7	1134.3	1115.3	1109.0
25°	1415.2	1397.7	1351.7	1286.6	1199.4	1153.4	1120.1	1086.7	1072.5	1059.8	1045.5
27.5°	1356.5	1313.6	1281.9	1196.2	1142.3	1089.9	1056.6	1031.2	1013.8	1001.1	990.0
30°	1283.5	1243.8	1199.4	1128.0	1078.8	1029.6	999.5	978.9	959.8	951.9	942.4
32.5°	1207.3	1170.8	1128.0	1070.9	1010.6	972.5	948.7	926.5	913.8	905.9	894.8
35°	1139.1	1093.1	1064.5	1010.6	961.4	918.6	896.4	877.3	863.1	859.9	858.3
37.5°	1066.1	1031.2	1004.3	948.7	907.5	871.0	850.4	829.7	821.8	820.2	813.9
40°	1002.7	972.5	947.1	894.8	850.4	817.0	801.2	788.5	780.6	780.6	779.0
42.5°	947.1	915.4	890.0	842.4	802.8	772.6	755.2	742.5	739.3	740.9	739.3
45°	885.3	858.3	832.9	783.7	750.4	728.2	709.2	702.8	698.1	699.6	701.2
47.5°	826.6	804.4	779.0	739.3	701.2	677.4	666.3	660.0	660.0	660.0	663.2
50°	774.2	748.8	726.6	685.4	650.5	631.4	621.9	614.0	615.6	617.1	618.7
52.5°	712.3	690.1	674.3	633.0	607.6	583.8	572.7	574.3	572.7	572.7	575.9
55°	658.4	636.2	620.3	582.2	556.9	541.0	531.5	526.7	528.3	525.1	531.5
57.5°	598.1	579.1	568.0	531.5	509.3	495.0	487.1	479.1	482.3	480.7	479.1
60°	545.8	523.5	506.1	480.7	461.7	444.2	439.5	431.5	434.7	431.5	429.9
62.5°	485.5	468.0	455.3	429.9	414.1	399.8	388.7	383.9	382.3	377.6	372.8
65°	425.2	415.7	403.0	377.6	361.7	350.6	344.3	339.5	337.9	325.2	311.0
67.5°	369.7	363.3	350.6	331.6	317.3	306.2	296.7	288.7	279.2	269.7	261.8
70°	317.3	307.8	299.8	282.4	269.7	258.6	249.1	239.6	234.8	225.3	222.1
72.5°	266.5	257.0	249.1	233.2	222.1	211.0	207.8	196.7	192.0	190.4	190.4
75°	214.2	206.2	201.5	187.2	177.7	169.8	165.0	161.8	158.6	155.5	150.7
77.5°	163.4	158.6	155.5	146.0	138.0	133.3	131.7	120.6	117.4	114.2	111.1
80°	119.0	117.4	114.2	106.3	103.1	92.0	92.0	88.8	87.3	87.3	87.3
82.5°	80.9	77.7	76.2	68.2	66.6	65.0	63.5	61.9	63.5	61.9	63.5
85°	42.8	41.2	39.7	39.7	39.7	39.7	39.7	39.7	39.7	38.1	39.7
87.5°	15.9	15.9	15.9	15.9	14.3	15.9	15.9	14.3	15.9	15.9	15.9
90°	6.1	6.1	6.1	10.6	10.6	12.1	13.6	12.9	13.6	14.4	15.1
92.5°	48.5	58.3	68.1	115.1	188.5	259.7	296.8	246.8	182.4	136.3	107.5
95°	62.8	78.7	94.6	160.5	284.6	465.6	617.0	634.4	561.0	443.6	342.2
97.5°	73.4	87.1	100.7	152.9	259.7	445.9	660.1	795.7	807.8	749.5	666.2
100°	86.3	98.4	110.5	155.2	240.7	395.2	608.7	802.5	913.0	928.1	891.0
102.5°	100.7	112.0	123.4	162.8	235.4	361.1	544.3	745.7	907.7	997.8	1020.5
105°	117.3	128.3	139.3	175.6	238.5	344.5	496.6	674.5	847.9	978.9	1053.8
107.5°	134.0	145.0	156.0	189.3	247.6	339.9	465.6	616.2	774.5	916.0	1020.5
110°	151.4	161.6	171.8	205.2	258.2	341.4	451.2	574.6	709.3	840.3	950.1

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4FO-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	168.1	178.3	188.5	220.3	269.5	346.0	444.4	551.1	661.7	773.7	875.9
115°	185.5	195.7	205.9	236.2	281.6	352.0	442.9	538.3	632.9	726.0	814.6
117.5°	201.4	212.0	222.6	251.3	293.7	358.1	442.1	531.4	616.2	695.0	766.9
120°	217.3	227.9	238.5	267.2	306.6	364.9	442.1	526.1	605.6	676.0	736.6
122.5°	233.2	243.4	253.6	282.4	318.7	371.7	441.4	520.1	596.5	663.9	717.7
125°	247.6	258.2	268.7	296.0	330.8	378.5	440.6	513.3	585.9	651.1	703.3
127.5°	261.2	271.8	282.4	308.9	341.4	383.8	439.1	504.2	573.8	636.7	688.9
130°	274.0	285.0	296.0	321.7	351.3	389.9	438.3	495.9	558.7	618.5	670.0
132.5°	286.2	296.4	306.6	332.3	361.1	395.2	437.6	488.3	542.8	598.1	648.0
135°	297.5	307.4	317.2	342.2	369.4	400.5	436.8	480.7	528.4	577.6	623.8
137.5°	307.4	316.8	326.3	349.8	375.5	403.5	436.8	473.9	514.8	557.9	598.1
140°	316.4	325.5	334.6	357.3	381.5	407.3	436.1	468.6	503.4	539.0	573.1
142.5°	324.8	333.5	342.2	364.1	386.1	410.3	436.1	464.1	492.8	523.1	551.1
145°	332.3	340.6	349.0	368.7	389.1	411.1	434.5	458.8	483.0	508.7	531.4
147.5°	339.9	347.5	355.1	374.0	392.1	411.8	432.3	454.2	474.7	495.9	514.8
150°	346.7	353.9	361.1	377.8	394.4	411.8	430.0	448.9	467.1	484.5	499.6
152.5°	353.5	360.0	366.4	380.8	395.9	410.3	426.2	442.9	458.8	473.2	486.8
155°	359.6	365.3	371.0	383.8	396.7	408.8	422.4	436.8	450.4	462.6	473.9
157.5°	365.7	370.2	374.7	386.1	396.7	407.3	418.6	430.8	441.4	452.0	461.8
160°	370.2	374.4	378.5	387.6	396.7	405.0	414.1	423.9	433.0	441.4	449.7
162.5°	374.7	377.8	380.8	389.1	396.7	402.7	409.6	417.9	424.7	431.5	437.6
165°	377.8	380.0	382.3	389.1	395.2	399.7	405.0	411.1	417.1	421.7	427.0
167.5°	380.0	381.9	383.8	389.1	393.7	396.7	400.5	405.0	409.6	413.3	417.9
170°	382.3	383.5	384.6	388.4	392.1	393.7	395.9	399.0	402.7	405.0	408.0
172.5°	383.8	384.6	385.3	387.6	390.6	390.6	391.4	393.7	396.7	398.2	399.7
175°	385.3	385.3	385.3	386.8	389.1	388.4	388.4	389.9	391.4	392.1	393.7
177.5°	385.3	385.3	385.3	386.1	387.6	386.1	386.1	386.8	387.6	388.4	388.4
180°	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8
2.5°	1861.0	1867.3	1859.4	1864.1	1853.0	1851.4	1853.0	1853.0	1854.6	1856.2	1857.8
5°	1756.3	1754.7	1745.1	1738.8	1734.0	1738.8	1742.0	1745.1	1742.0	1745.1	1746.7
7.5°	1657.9	1653.1	1648.4	1637.3	1640.4	1637.3	1646.8	1642.0	1642.0	1650.0	1656.3
10°	1570.6	1561.1	1557.9	1545.2	1535.7	1534.1	1545.2	1550.0	1554.8	1557.9	1570.6
12.5°	1458.0	1443.7	1432.6	1437.4	1410.4	1421.5	1424.7	1418.3	1437.4	1459.6	1446.9
15°	1337.4	1339.0	1316.8	1308.9	1286.6	1293.0	1294.6	1310.4	1326.3	1324.7	1343.8
17.5°	1248.6	1239.1	1220.0	1218.4	1208.9	1213.7	1212.1	1224.8	1220.0	1227.9	1243.8
20°	1166.1	1159.7	1143.9	1137.5	1140.7	1137.5	1139.1	1140.7	1145.5	1162.9	1159.7
22.5°	1101.0	1093.1	1093.1	1085.2	1075.6	1072.5	1080.4	1085.2	1091.5	1094.7	1102.6
25°	1043.9	1037.6	1029.6	1024.9	1016.9	1018.5	1023.3	1029.6	1034.4	1040.7	1047.1
27.5°	985.2	985.2	977.3	975.7	972.5	970.9	977.3	980.5	980.5	985.2	991.6
30°	939.2	939.2	931.3	929.7	928.1	928.1	932.9	934.4	936.0	940.8	944.0
32.5°	894.8	893.2	890.0	891.6	890.0	891.6	891.6	893.2	896.4	898.0	904.3
35°	853.5	855.1	851.9	851.9	850.4	851.9	855.1	856.7	858.3	861.5	861.5
37.5°	813.9	817.0	815.5	820.2	820.2	820.2	820.2	823.4	823.4	823.4	821.8
40°	779.0	779.0	777.4	780.6	783.7	783.7	785.3	785.3	786.9	786.9	785.3
42.5°	739.3	742.5	747.2	748.8	752.0	750.4	755.2	753.6	755.2	752.0	748.8
45°	702.8	702.8	709.2	715.5	717.1	717.1	717.1	720.3	717.1	712.3	710.8
47.5°	663.2	666.3	669.5	677.4	679.0	679.0	679.0	679.0	675.8	675.8	675.8
50°	623.5	625.1	626.7	629.8	634.6	633.0	633.0	633.0	639.4	633.0	634.6
52.5°	575.9	577.5	579.1	585.4	583.8	583.8	585.4	585.4	590.2	588.6	585.4
55°	528.3	528.3	531.5	531.5	531.5	534.6	536.2	539.4	537.8	539.4	541.0
57.5°	480.7	477.5	475.9	475.9	480.7	479.1	480.7	480.7	487.1	490.2	491.8
60°	425.2	425.2	423.6	414.1	414.1	412.5	417.2	420.4	423.6	437.9	436.3
62.5°	368.1	361.7	355.4	357.0	347.4	352.2	349.0	352.2	361.7	372.8	374.4
65°	311.0	306.2	299.8	298.3	295.1	299.8	298.3	299.8	304.6	311.0	318.9
67.5°	260.2	258.6	255.4	253.8	253.8	253.8	257.0	257.0	258.6	263.4	268.1
70°	222.1	220.5	222.1	218.9	220.5	218.9	220.5	222.1	223.7	225.3	230.0
72.5°	187.2	187.2	187.2	184.0	187.2	185.6	185.6	187.2	188.8	190.4	193.6
75°	149.1	146.0	142.8	139.6	138.0	141.2	142.8	141.2	146.0	152.3	152.3
77.5°	112.6	111.1	111.1	111.1	112.6	111.1	114.2	112.6	114.2	114.2	117.4
80°	87.3	85.7	87.3	87.3	85.7	88.8	87.3	87.3	88.8	90.4	88.8
82.5°	63.5	65.0	63.5	63.5	63.5	66.6	63.5	63.5	63.5	65.0	65.0
85°	39.7	39.7	39.7	39.7	41.2	39.7	41.2	39.7	42.8	41.2	41.2
87.5°	14.3	15.9	17.5	17.5	17.5	17.5	15.9	17.5	19.0	17.5	19.0
90°	15.1	15.1	15.9	16.7	15.9	15.9	15.9	16.7	15.9	15.1	15.1
92.5°	98.0	88.6	77.2	71.9	68.9	68.9	68.9	71.9	77.2	88.6	98.0
95°	305.4	268.7	231.7	208.2	194.6	184.7	194.6	208.2	231.7	268.7	305.4
97.5°	623.8	581.4	529.9	484.5	461.8	443.6	461.8	484.5	529.9	581.4	623.8
100°	863.0	835.0	769.2	723.0	700.3	694.2	700.3	723.0	769.2	835.0	863.0
102.5°	1013.0	1005.4	971.3	941.0	916.8	912.2	916.8	941.0	971.3	1005.4	1013.0
105°	1069.3	1084.8	1086.4	1080.3	1069.7	1065.2	1069.7	1080.3	1086.4	1084.8	1069.3
107.5°	1052.3	1084.1	1117.4	1131.0	1137.1	1137.8	1137.1	1131.0	1117.4	1084.1	1052.3
110°	991.8	1033.4	1087.1	1118.9	1132.5	1139.3	1132.5	1118.9	1087.1	1033.4	991.8

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	917.6	959.2	1022.0	1062.1	1082.6	1094.7	1082.6	1062.1	1022.0	959.2	917.6
115°	851.0	887.3	947.1	992.5	1016.7	1022.8	1016.7	992.5	947.1	887.3	851.0
117.5°	798.7	830.5	883.5	922.8	948.6	952.4	948.6	922.8	883.5	830.5	798.7
120°	763.5	790.4	833.5	866.8	886.5	894.8	886.5	866.8	833.5	790.4	763.5
122.5°	740.4	763.1	797.9	825.2	841.1	849.4	841.1	825.2	797.9	763.1	740.4
125°	724.1	744.9	775.2	797.2	811.5	816.1	811.5	797.2	775.2	744.9	724.1
127.5°	708.6	728.3	758.6	778.2	790.4	794.9	790.4	778.2	758.6	728.3	708.6
130°	690.0	710.1	741.1	760.1	772.2	776.7	772.2	760.1	741.1	710.1	690.0
132.5°	668.1	688.2	718.4	740.4	751.7	756.3	751.7	740.4	718.4	688.2	668.1
135°	642.8	661.7	691.9	713.1	725.2	729.8	725.2	713.1	691.9	661.7	642.8
137.5°	615.5	632.9	661.7	683.6	693.4	698.7	693.4	683.6	661.7	632.9	615.5
140°	589.0	604.9	631.4	648.0	658.6	664.7	658.6	648.0	631.4	604.9	589.0
142.5°	564.4	577.6	600.3	615.5	624.6	628.3	624.6	615.5	600.3	577.6	564.4
145°	542.0	552.6	571.6	584.4	592.0	595.8	592.0	584.4	571.6	552.6	542.0
147.5°	523.5	532.2	546.6	557.9	564.0	565.5	564.0	557.9	546.6	532.2	523.5
150°	506.4	513.3	525.4	535.2	539.8	540.5	539.8	535.2	525.4	513.3	506.4
152.5°	492.1	497.4	507.2	514.8	517.1	517.8	517.1	514.8	507.2	497.4	492.1
155°	478.4	483.0	490.6	496.6	498.9	498.9	498.9	496.6	490.6	483.0	478.4
157.5°	465.6	469.4	475.4	480.0	481.5	481.5	481.5	480.0	475.4	469.4	465.6
160°	452.7	455.7	460.3	464.8	465.6	465.6	465.6	464.8	460.3	455.7	452.7
162.5°	440.2	442.9	445.9	450.4	451.2	450.4	451.2	450.4	445.9	442.9	440.2
165°	428.9	430.8	433.8	436.8	436.1	435.3	436.1	436.8	433.8	430.8	428.9
167.5°	419.0	420.2	421.7	423.9	423.9	423.2	423.9	423.9	421.7	420.2	419.0
170°	409.2	410.3	411.8	412.6	411.8	411.8	411.8	412.6	411.8	410.3	409.2
172.5°	400.4	401.2	402.0	402.7	402.0	400.5	402.0	402.7	402.0	401.2	400.4
175°	393.7	393.7	393.7	395.2	393.7	392.1	393.7	395.2	393.7	393.7	393.7
177.5°	388.8	389.1	388.4	389.1	387.6	386.1	387.6	389.1	388.4	389.1	388.8
180°	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8	1968.8
2.5°	1864.1	1872.1	1868.9	1857.8	1862.5	1872.1	1881.6	1894.3	1902.2	1908.6	1911.7
5°	1754.7	1768.9	1765.8	1765.8	1772.1	1788.0	1803.8	1830.8	1840.3	1851.4	1867.3
7.5°	1657.9	1669.0	1678.5	1681.7	1691.2	1711.8	1732.5	1762.6	1786.4	1799.1	1808.6
10°	1572.2	1580.1	1594.4	1602.4	1611.9	1637.3	1667.4	1699.1	1722.9	1745.1	1757.8
12.5°	1462.7	1494.5	1513.5	1526.2	1538.9	1577.0	1600.8	1635.7	1664.2	1684.9	1703.9
15°	1340.6	1378.7	1389.8	1439.0	1470.7	1500.8	1537.3	1578.6	1605.5	1629.3	1654.7
17.5°	1237.5	1264.4	1277.1	1329.5	1356.5	1404.0	1456.4	1508.8	1550.0	1567.5	1592.8
20°	1172.4	1186.7	1212.1	1229.5	1258.1	1313.6	1370.7	1434.2	1496.1	1513.5	1538.9
22.5°	1105.8	1124.8	1142.3	1166.1	1188.3	1226.4	1283.5	1353.3	1419.9	1451.6	1481.8
25°	1045.5	1064.5	1075.6	1101.0	1121.7	1159.7	1199.4	1270.8	1350.1	1377.1	1424.7
27.5°	997.9	1009.0	1028.0	1039.2	1063.0	1097.9	1134.3	1188.3	1266.0	1312.0	1358.0
30°	950.3	958.2	974.1	990.0	1007.4	1031.2	1072.5	1124.8	1196.2	1235.9	1281.9
32.5°	902.7	915.4	924.9	936.0	955.1	983.6	1012.2	1063.0	1120.1	1164.5	1210.5
35°	863.1	867.8	880.5	893.2	905.9	931.3	961.4	1010.6	1061.4	1096.3	1137.5
37.5°	820.2	828.2	837.7	842.4	863.1	878.9	910.6	948.7	1009.0	1031.2	1072.5
40°	786.9	785.3	794.8	802.8	812.3	837.7	856.7	898.0	945.6	980.5	1005.8
42.5°	745.7	745.7	748.8	758.3	771.0	786.9	809.1	844.0	893.2	918.6	948.7
45°	712.3	707.6	709.2	715.5	723.4	739.3	761.5	791.7	840.8	861.5	893.2
47.5°	672.7	667.9	667.9	674.3	680.6	691.7	709.2	744.1	783.7	810.7	834.5
50°	628.3	629.8	628.3	633.0	636.2	647.3	666.3	694.9	731.4	753.6	780.6
52.5°	587.0	583.8	582.2	585.4	591.8	599.7	620.3	645.7	680.6	702.8	726.6
55°	536.2	539.4	539.4	539.4	548.9	552.1	568.0	593.3	628.3	645.7	667.9
57.5°	490.2	488.6	491.8	490.2	498.2	509.3	522.0	541.0	575.9	593.3	614.0
60°	439.5	441.0	442.6	442.6	449.0	460.1	474.4	491.8	520.4	537.8	556.9
62.5°	377.6	385.5	393.5	396.6	406.1	414.1	423.6	442.6	468.0	480.7	498.2
65°	318.9	330.0	341.1	349.0	355.4	363.3	376.0	393.5	414.1	426.8	444.2
67.5°	268.1	276.1	290.3	298.3	311.0	320.5	328.4	342.7	368.1	372.8	387.1
70°	231.6	234.8	241.1	247.5	261.8	269.7	279.2	293.5	312.5	323.6	331.6
72.5°	195.1	196.7	199.9	206.2	212.6	222.1	233.2	245.9	263.4	268.1	279.2
75°	155.5	165.0	165.0	169.8	174.5	179.3	188.8	201.5	212.6	220.5	226.9
77.5°	115.8	120.6	123.7	131.7	138.0	142.8	149.1	158.6	165.0	171.3	176.1
80°	90.4	92.0	93.6	93.6	96.8	103.1	109.5	115.8	123.7	126.9	131.7
82.5°	66.6	66.6	66.6	69.8	71.4	73.0	73.0	76.2	84.1	87.3	92.0
85°	42.8	42.8	42.8	42.8	44.4	46.0	47.6	49.2	49.2	49.2	52.4
87.5°	17.5	20.6	19.0	20.6	20.6	20.6	20.6	22.2	22.2	23.8	23.8
90°	15.1	14.4	13.6	12.9	13.6	12.1	10.6	10.6	6.1	6.1	6.1
92.5°	107.5	136.3	182.4	246.8	296.8	259.7	188.5	115.1	68.1	58.3	48.5
95°	342.2	443.6	561.0	634.4	617.0	465.6	284.6	160.5	94.6	78.7	62.8
97.5°	666.2	749.5	807.8	795.7	660.1	445.9	259.7	152.9	100.7	87.1	73.4
100°	891.0	928.1	913.0	802.5	608.7	395.2	240.7	155.2	110.5	98.4	86.3
102.5°	1020.5	997.8	907.7	745.7	544.3	361.1	235.4	162.8	123.4	112.0	100.7
105°	1053.8	978.9	847.9	674.5	496.6	344.5	238.5	175.6	139.3	128.3	117.3
107.5°	1020.5	916.0	774.5	616.2	465.6	339.9	247.6	189.3	156.0	145.0	134.0
110°	950.1	840.3	709.3	574.6	451.2	341.4	258.2	205.2	171.8	161.6	151.4

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	875.9	773.7	661.7	551.1	444.4	346.0	269.5	220.3	188.5	178.3	168.1
115°	814.6	726.0	632.9	538.3	442.9	352.0	281.6	236.2	205.9	195.7	185.5
117.5°	766.9	695.0	616.2	531.4	442.1	358.1	293.7	251.3	222.6	212.0	201.4
120°	736.6	676.0	605.6	526.1	442.1	364.9	306.6	267.2	238.5	227.9	217.3
122.5°	717.7	663.9	596.5	520.1	441.4	371.7	318.7	282.4	253.6	243.4	233.2
125°	703.3	651.1	585.9	513.3	440.6	378.5	330.8	296.0	268.7	258.2	247.6
127.5°	688.9	636.7	573.8	504.2	439.1	383.8	341.4	308.9	282.4	271.8	261.2
130°	670.0	618.5	558.7	495.9	438.3	389.9	351.3	321.7	296.0	285.0	274.0
132.5°	648.0	598.1	542.8	488.3	437.6	395.2	361.1	332.3	306.6	296.4	286.2
135°	623.8	577.6	528.4	480.7	436.8	400.5	369.4	342.2	317.2	307.4	297.5
137.5°	598.1	557.9	514.8	473.9	436.8	403.5	375.5	349.8	326.3	316.8	307.4
140°	573.1	539.0	503.4	468.6	436.1	407.3	381.5	357.3	334.6	325.5	316.4
142.5°	551.1	523.1	492.8	464.1	436.1	410.3	386.1	364.1	342.2	333.5	324.8
145°	531.4	508.7	483.0	458.8	434.5	411.1	389.1	368.7	349.0	340.6	332.3
147.5°	514.8	495.9	474.7	454.2	432.3	411.8	392.1	374.0	355.1	347.5	339.9
150°	499.6	484.5	467.1	448.9	430.0	411.8	394.4	377.8	361.1	353.9	346.7
152.5°	486.8	473.2	458.8	442.9	426.2	410.3	395.9	380.8	366.4	360.0	353.5
155°	473.9	462.6	450.4	436.8	422.4	408.8	396.7	383.8	371.0	365.3	359.6
157.5°	461.8	452.0	441.4	430.8	418.6	407.3	396.7	386.1	374.7	370.2	365.7
160°	449.7	441.4	433.0	423.9	414.1	405.0	396.7	387.6	378.5	374.4	370.2
162.5°	437.6	431.5	424.7	417.9	409.6	402.7	396.7	389.1	380.8	377.8	374.7
165°	427.0	421.7	417.1	411.1	405.0	399.7	395.2	389.1	382.3	380.0	377.8
167.5°	417.9	413.3	409.6	405.0	400.5	396.7	393.7	389.1	383.8	381.9	380.0
170°	408.0	405.0	402.7	399.0	395.9	393.7	392.1	388.4	384.6	383.5	382.3
172.5°	399.7	398.2	396.7	393.7	391.4	390.6	390.6	387.6	385.3	384.6	383.8
175°	393.7	392.1	391.4	389.9	388.4	388.4	389.1	386.8	385.3	385.3	385.3
177.5°	388.4	388.4	387.6	386.8	386.1	386.1	387.6	386.1	385.3	385.3	385.3
180°	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3	385.3

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1968.8	1968.8	1968.8	1968.8
2.5°	1924.4	1933.9	1949.8	1972.0
5°	1880.0	1907.0	1932.4	1965.7
7.5°	1840.3	1872.1	1907.0	1954.6
10°	1794.3	1834.0	1878.4	1937.1
12.5°	1740.4	1795.9	1846.7	1910.1
15°	1700.7	1742.0	1807.0	1881.6
17.5°	1645.2	1700.7	1765.8	1849.9
20°	1592.8	1651.5	1724.5	1811.8
22.5°	1537.3	1603.9	1676.9	1770.5
25°	1480.2	1551.6	1624.6	1724.5
27.5°	1427.8	1492.9	1575.4	1676.9
30°	1364.4	1439.0	1518.3	1624.6
32.5°	1302.5	1380.3	1461.2	1567.5
35°	1235.9	1313.6	1402.5	1504.0
37.5°	1170.8	1256.5	1337.4	1435.8
40°	1099.4	1188.3	1272.4	1372.3
42.5°	1029.6	1121.7	1205.7	1291.4
45°	964.6	1055.0	1131.2	1212.1
47.5°	902.7	983.6	1061.4	1134.3
50°	842.4	910.6	982.0	1042.3
52.5°	779.0	844.0	901.1	955.1
55°	721.9	772.6	823.4	872.6
57.5°	653.6	704.4	748.8	786.9
60°	596.5	628.3	671.1	710.8
62.5°	531.5	568.0	601.3	626.7
65°	468.0	499.7	525.1	547.3
67.5°	414.1	433.1	452.2	475.9
70°	349.0	364.9	387.1	404.6
72.5°	293.5	306.2	317.3	337.9
75°	238.0	249.1	255.4	274.5
77.5°	184.0	195.1	199.9	211.0
80°	141.2	142.8	149.1	158.6
82.5°	96.8	99.9	101.5	109.5
85°	55.5	63.5	61.9	65.0
87.5°	23.8	25.4	28.6	31.7
90°	5.3	4.5	2.3	0.8
92.5°	34.8	23.5	15.1	10.6
95°	44.7	34.8	27.3	25.0
97.5°	57.5	48.5	41.6	41.6
100°	71.9	62.8	57.5	57.5
102.5°	87.1	78.7	74.2	72.7
105°	103.7	94.6	90.8	88.6
107.5°	121.1	111.3	107.5	106.0
110°	137.8	128.7	124.9	123.4

TEST NUMBER: P1026201

CATALOG NUMBER: S124RDIP-B1195D810UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	154.4	146.1	141.6	140.1
115°	171.1	163.5	158.2	156.0
117.5°	187.7	179.4	174.9	172.6
120°	204.4	196.1	190.8	189.3
122.5°	218.8	211.2	205.9	204.4
125°	233.2	224.8	220.3	217.3
127.5°	246.0	237.0	231.7	229.4
130°	259.7	248.3	242.3	239.2
132.5°	270.3	259.7	251.3	249.1
135°	281.6	268.7	261.2	258.2
137.5°	290.7	278.6	270.3	267.2
140°	300.5	287.7	279.3	277.1
142.5°	309.6	297.5	289.9	287.7
145°	318.0	307.4	299.8	297.5
147.5°	327.8	316.4	309.6	308.9
150°	335.4	326.3	320.2	319.5
152.5°	343.7	335.4	329.3	329.3
155°	351.3	343.7	339.2	338.4
157.5°	358.1	352.0	347.5	347.5
160°	364.1	358.8	355.8	355.8
162.5°	369.4	364.9	362.6	363.4
165°	374.0	370.2	368.7	368.7
167.5°	377.8	374.7	374.0	374.7
170°	380.8	378.5	377.8	378.5
172.5°	383.1	381.5	381.5	382.3
175°	384.6	383.8	383.8	384.6
177.5°	385.3	384.6	385.3	386.1
180°	385.3	385.3	385.3	385.3

(END OF REPORT)