

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026273

Luminaire Tested: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026273
REPORT IS A COMBINATION OF REPORTS P999283 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5778.0 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33
1	92	88	85	81	82	79	76	73	61	59	57	45	44	42	30	29	29
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	26	25	24
3	77	68	61	56	68	61	55	51	48	44	40	35	33	30	24	22	21
4	70	60	53	47	63	54	48	43	42	38	34	31	29	26	21	20	18
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	17	16
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	16	14
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11
9	47	36	28	24	42	32	26	22	26	21	18	19	16	14	13	12	10
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4684	4684	4684	4684
5°	4684	5292	4692	4045
10°	4659	6101	4655	3518
15°	4603	6866	4603	2945
20°	4546	7445	4522	2594
25°	4474	7477	4454	2342
30°	4400	6357	4365	2170
35°	4293	4797	4238	2041
40°	4175	3476	4092	1940
45°	3978	2642	3879	1851
50°	3746	2135	3644	1721
55°	3495	1768	3380	1548
60°	3242	1495	3097	1287
65°	2925	1217	2831	1023
70°	2633	987	2510	831
75°	2308	711	2147	609
80°	1904	472	1732	447
85°	1383	243	1142	243

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 5864 cd/sqm

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	1.0
10°-20°	168.0	2.9
20°-30°	263.1	4.6
30°-40°	292.2	5.1
40°-50°	258.9	4.5
50°-60°	201.8	3.5
60°-70°	132.0	2.3
70°-80°	64.8	1.1
80°-90°	18.1	0.3
90°-100°	430.2	7.4
100°-110°	898.3	15.5
110°-120°	798.5	13.8
120°-130°	672.1	11.6
130°-140°	560.8	9.7
140°-150°	428.1	7.4
150°-160°	301.0	5.2
160°-170°	177.0	3.1
170°-180°	57.6	1.0
0°-30°	486.7	8.4
0°-40°	778.8	13.5
0°-60°	1239.5	21.5
0°-90°	1454.3	25.2
90°-120°	2127.0	36.8
90°-150°	3788.0	65.6
90°-180°	4324.0	74.8
0°-180°	5778.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	574	574	574	574	574	
5°	574	664	574	507	574	54
15°	549	879	549	377	549	155
25°	503	948	501	297	503	232
35°	439	584	433	248	439	274
45°	354	298	345	209	354	273
55°	255	178	246	156	255	228
65°	160	104	155	88	160	159
75°	80	48	74	41	80	85
85°	19	12	16	12	19	21
90°	1	24	1	24	1	4
95°	38	285	38	285	38	42
105°	136	1641	136	1641	136	145
115°	240	1576	240	1576	240	238
125°	335	1257	335	1257	335	298
135°	398	1124	398	1124	398	307
145°	458	918	458	918	458	288
155°	521	769	521	769	521	240
165°	568	671	568	671	568	160
175°	592	604	592	604	592	56
180°	594	594	594	594	594	

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4
2.5°	575.3	580.4	583.2	585.5	590.1	592.0	595.7	596.6	600.3	599.9	598.5
5°	573.5	582.3	588.7	595.7	604.0	608.6	613.7	621.1	624.8	629.9	633.2
7.5°	570.2	582.3	592.9	603.6	617.0	624.4	630.9	642.4	652.2	660.5	669.7
10°	565.1	580.4	596.1	610.5	629.0	637.8	647.5	664.6	678.1	689.6	704.5
12.5°	557.3	578.6	596.1	615.6	639.2	651.2	664.2	684.6	700.3	719.3	737.8
15°	548.9	572.5	595.7	621.1	648.0	661.9	674.8	702.1	726.2	748.0	768.3
17.5°	539.7	565.6	591.1	619.3	651.7	668.8	684.1	717.0	743.3	771.6	791.9
20°	528.6	556.8	586.0	617.4	654.0	673.0	690.1	727.6	756.8	787.3	812.8
22.5°	516.5	547.1	579.0	613.3	651.2	672.1	692.0	732.2	766.0	794.2	828.5
25°	503.1	535.5	568.4	604.5	647.1	669.7	690.1	729.9	766.0	803.0	836.4
27.5°	489.2	522.6	556.8	594.8	638.3	660.5	683.6	722.0	764.2	804.4	838.2
30°	474.0	506.4	542.5	578.6	624.8	647.1	670.7	712.3	758.1	798.4	835.0
32.5°	457.3	490.6	524.9	562.4	607.7	631.8	653.5	700.8	747.5	787.3	821.6
35°	438.8	470.3	502.7	541.1	586.0	607.7	633.6	682.7	729.9	772.0	794.2
37.5°	418.9	449.0	479.0	517.0	560.0	586.4	611.9	661.4	711.4	739.6	751.2
40°	400.4	426.7	453.1	489.7	533.2	560.5	586.4	637.8	681.8	703.5	694.7
42.5°	376.8	404.1	427.7	461.5	505.4	530.9	557.3	610.5	646.1	654.9	633.2
45°	353.6	376.3	399.0	431.8	478.1	499.9	528.1	577.6	607.3	599.4	567.5
47.5°	330.9	349.4	370.7	402.7	444.3	470.3	496.6	539.7	560.5	549.4	505.0
50°	304.1	322.6	344.8	372.6	412.9	437.9	458.7	498.5	514.2	486.9	433.2
52.5°	278.6	294.8	313.8	339.7	378.1	400.8	423.5	457.8	462.8	431.4	374.9
55°	254.6	267.5	287.4	308.3	343.4	367.5	383.2	412.4	411.0	371.7	323.1
57.5°	229.6	241.6	255.0	276.8	310.1	328.2	345.3	370.7	357.3	324.0	275.9
60°	207.4	214.3	227.7	248.5	276.8	292.5	305.9	319.8	308.3	272.2	235.1
62.5°	182.8	190.7	200.4	217.1	242.1	256.9	266.6	272.6	260.6	232.8	199.0
65°	159.7	166.6	176.8	191.6	210.6	221.7	226.8	231.0	224.5	193.0	166.2
67.5°	138.9	143.5	152.7	162.5	182.8	185.6	192.5	194.4	181.4	157.4	136.1
70°	118.0	122.7	126.8	138.4	147.6	152.7	154.1	154.1	141.2	125.4	107.8
72.5°	98.6	101.4	105.5	113.4	118.5	122.2	124.0	121.7	109.7	96.7	83.8
75°	80.1	81.5	85.2	90.3	94.4	93.0	92.6	89.8	81.0	71.7	64.3
77.5°	61.6	62.5	66.7	68.0	68.0	69.4	67.6	64.8	57.4	50.5	47.2
80°	46.3	47.7	48.1	49.1	48.1	48.1	46.7	42.1	38.4	35.2	32.9
82.5°	31.9	32.9	33.3	31.9	32.9	31.5	29.2	25.9	23.6	23.1	22.2
85°	19.0	19.4	19.0	19.0	17.6	17.1	15.3	14.8	13.9	13.9	13.4
87.5°	9.3	8.8	7.9	6.9	6.9	6.5	6.9	6.0	6.9	6.5	6.0
90°	1.2	3.5	7.0	8.2	9.3	9.3	9.3	16.3	16.3	18.7	21.0
92.5°	16.3	23.3	36.2	53.6	74.6	89.8	105.0	177.3	290.4	400.0	457.2
95°	38.5	42.0	53.6	68.8	96.8	121.3	145.8	247.3	438.5	717.3	950.5
97.5°	64.1	64.1	74.6	88.6	113.1	134.1	155.1	235.6	400.0	686.9	1017.0
100°	88.6	88.6	96.8	110.8	133.0	151.6	170.3	239.1	370.9	608.8	937.7
102.5°	112.0	114.3	121.3	134.1	155.1	172.6	190.1	250.8	362.7	556.3	838.6
105°	136.5	140.0	145.8	159.8	180.8	197.7	214.6	270.6	367.4	530.7	765.1
107.5°	163.3	165.6	171.4	186.6	206.4	223.4	240.3	291.6	381.4	523.7	717.3
110°	190.1	192.4	198.3	212.3	233.3	249.0	264.7	316.1	397.7	526.0	695.1

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	215.8	218.1	225.1	237.9	258.9	274.6	290.4	339.4	415.2	533.0	684.6
115°	240.3	243.8	251.9	263.6	285.7	301.4	317.2	363.9	433.9	542.3	682.3
117.5°	265.9	269.4	276.4	289.2	310.2	326.5	342.9	387.2	452.5	551.7	681.1
120°	291.6	293.9	302.1	314.9	334.7	351.0	367.4	411.7	472.3	562.2	681.1
122.5°	314.9	317.2	325.4	337.1	359.2	375.0	390.7	435.0	491.0	572.7	680.0
125°	334.7	339.4	346.4	359.2	381.4	397.7	414.0	456.0	509.7	583.1	678.8
127.5°	353.4	356.9	365.1	379.0	402.4	418.7	435.0	475.8	526.0	591.3	676.5
130°	368.5	373.2	382.5	400.0	422.2	439.1	456.0	495.7	541.2	600.6	675.3
132.5°	383.7	387.2	400.0	416.4	440.9	456.6	472.3	512.0	556.3	608.8	674.1
135°	397.7	402.4	414.0	433.9	458.4	473.6	488.7	527.2	569.2	617.0	673.0
137.5°	411.7	416.4	429.2	447.9	473.5	488.1	502.7	538.8	578.5	621.6	673.0
140°	426.9	430.4	443.2	463.0	487.5	501.5	515.5	550.5	587.8	627.5	671.8
142.5°	443.2	446.7	458.4	477.0	500.3	513.8	527.2	561.0	594.8	632.1	671.8
145°	458.4	461.9	473.5	489.8	512.0	524.8	537.7	568.0	599.5	633.3	669.5
147.5°	475.8	477.0	487.5	505.0	523.7	535.4	547.0	576.2	604.1	634.5	666.0
150°	492.2	493.3	502.7	516.7	534.2	545.2	556.3	582.0	607.6	634.5	662.5
152.5°	507.3	507.3	516.7	529.5	544.7	554.6	564.5	586.6	610.0	632.1	656.6
155°	521.3	522.5	529.5	541.2	554.0	562.8	571.5	591.3	611.1	629.8	650.8
157.5°	535.3	535.3	542.3	551.7	563.3	570.3	577.3	594.8	611.1	627.5	645.0
160°	548.2	548.2	552.8	561.0	570.3	576.7	583.1	597.1	611.1	624.0	638.0
162.5°	559.8	558.7	562.2	569.2	577.3	582.0	586.6	599.5	611.1	620.5	631.0
165°	568.0	568.0	570.3	576.2	582.0	585.5	589.0	599.5	608.8	615.8	624.0
167.5°	577.3	576.2	577.3	582.0	585.5	588.4	591.3	599.5	606.5	611.1	617.0
170°	583.1	582.0	583.1	586.6	589.0	590.8	592.5	598.3	604.1	606.5	610.0
172.5°	589.0	587.8	587.8	590.1	591.3	592.4	593.6	597.1	601.8	601.8	603.0
175°	592.5	591.3	591.3	592.5	593.6	593.6	593.6	596.0	599.5	598.3	598.3
177.5°	594.8	593.6	592.5	593.6	593.6	593.6	593.6	594.8	597.1	594.8	594.8
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4
2.5°	602.2	607.3	607.7	612.3	611.0	608.6	612.8	610.0	615.6	613.7	616.1
5°	637.3	644.3	650.3	654.0	660.5	659.1	666.0	663.7	668.8	663.7	670.2
7.5°	678.5	690.1	696.1	705.8	708.6	709.1	717.4	719.3	722.5	719.3	723.0
10°	718.8	732.7	746.6	754.4	759.5	766.5	773.9	777.1	779.4	776.2	778.5
12.5°	755.4	777.1	792.4	808.1	811.8	817.9	825.7	824.8	834.1	832.2	836.4
15°	789.2	813.2	831.7	844.2	854.4	859.5	874.3	875.2	874.8	879.4	876.6
17.5°	819.2	839.6	866.0	882.2	894.7	894.7	903.0	920.1	918.8	918.3	921.1
20°	843.8	866.9	891.4	918.8	928.9	930.8	942.4	951.2	952.5	952.5	952.5
22.5°	862.3	889.6	916.0	935.4	943.3	949.8	959.9	965.5	967.4	966.4	967.4
25°	871.5	897.5	924.3	941.9	946.5	950.2	951.2	954.4	953.9	948.4	951.6
27.5°	873.4	898.4	916.0	920.6	918.3	916.0	901.2	902.6	898.4	890.1	893.3
30°	865.1	878.5	878.0	863.7	859.5	849.8	836.4	816.5	800.3	793.3	795.6
32.5°	835.0	835.0	818.3	785.9	771.6	754.0	729.9	711.9	690.6	685.9	694.7
35°	793.3	769.7	739.2	696.6	674.8	661.9	620.2	607.3	589.2	584.1	588.3
37.5°	728.5	689.2	644.7	604.9	586.4	563.3	526.7	508.2	495.2	486.5	490.6
40°	655.9	608.2	561.9	512.8	492.5	473.5	446.2	429.5	408.7	409.6	411.0
42.5°	586.4	530.4	478.6	433.2	413.8	398.0	379.1	358.7	351.3	349.0	346.7
45°	512.8	453.1	404.5	370.7	353.2	338.3	320.8	309.2	300.4	298.5	300.9
47.5°	443.4	393.0	346.7	315.2	300.9	293.4	279.6	268.9	263.4	258.7	261.5
50°	380.5	333.3	296.2	269.8	259.7	254.6	241.6	236.1	230.5	229.1	228.6
52.5°	328.6	288.4	256.4	235.1	227.3	224.5	214.8	206.9	202.3	203.7	204.6
55°	281.4	247.2	222.2	205.0	198.6	195.3	188.4	182.8	179.6	178.2	179.1
57.5°	239.8	210.1	192.1	178.2	173.1	171.7	164.3	162.5	160.1	158.8	158.8
60°	201.8	181.0	164.3	156.4	150.9	149.5	143.9	141.6	141.2	139.8	138.9
62.5°	169.9	152.7	141.2	132.8	130.5	130.1	126.4	123.6	122.2	121.3	121.3
65°	142.1	129.6	119.9	113.9	112.0	111.1	106.9	106.0	105.1	104.1	103.7
67.5°	118.5	107.4	100.4	96.3	94.0	94.4	92.1	90.3	90.3	89.8	89.3
70°	95.8	88.9	82.8	80.5	79.6	78.7	77.8	76.4	75.9	75.9	75.9
72.5°	75.4	70.8	67.6	66.2	65.3	64.3	63.4	63.4	63.4	62.9	62.9
75°	57.9	56.0	53.7	52.3	52.3	53.2	51.8	50.5	49.1	48.1	48.6
77.5°	43.5	42.6	41.2	38.9	39.3	38.4	38.4	37.5	38.0	38.0	37.0
80°	31.9	30.5	30.1	28.7	29.2	28.7	28.2	28.2	27.3	27.3	27.3
82.5°	22.2	20.8	20.8	20.4	19.9	19.9	19.4	19.4	19.9	19.0	19.0
85°	13.4	13.0	13.0	12.0	12.0	12.0	12.0	12.5	12.0	11.6	11.6
87.5°	6.0	6.5	6.0	5.6	5.6	5.6	5.1	5.1	4.6	5.1	5.1
90°	19.8	21.0	22.2	23.3	23.3	23.3	24.5	25.7	24.5	24.5	24.5
92.5°	380.2	281.1	209.9	165.6	151.0	136.5	119.0	110.8	106.1	106.1	106.1
95°	977.4	864.2	683.4	527.2	470.6	414.0	356.9	320.7	299.7	284.6	299.7
97.5°	1225.8	1244.4	1154.6	1026.3	961.0	895.7	816.4	746.4	711.4	683.4	711.4
100°	1236.3	1406.6	1429.9	1372.7	1329.6	1286.4	1185.0	1113.8	1078.8	1069.5	1078.8
102.5°	1148.8	1398.4	1537.2	1572.2	1560.5	1548.8	1496.4	1449.7	1412.4	1405.4	1412.4
105°	1039.2	1306.3	1508.0	1623.5	1647.4	1671.3	1673.6	1664.3	1648.0	1641.0	1648.0
107.5°	949.4	1193.1	1411.2	1572.2	1621.2	1670.1	1721.5	1742.4	1751.8	1752.9	1751.8
110°	885.2	1092.8	1294.6	1463.7	1527.8	1592.0	1674.8	1723.8	1744.8	1755.3	1744.8

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	849.1	1019.3	1192.0	1349.4	1413.6	1477.7	1574.5	1636.3	1667.8	1686.5	1667.8
115°	829.2	975.0	1118.5	1254.9	1310.9	1366.9	1459.0	1529.0	1566.3	1575.7	1566.3
117.5°	818.7	949.4	1070.7	1181.5	1230.4	1279.4	1361.1	1421.7	1461.4	1467.2	1461.4
120°	810.6	933.0	1041.5	1134.8	1176.2	1217.6	1284.1	1335.4	1365.7	1378.6	1365.7
122.5°	801.2	919.0	1022.8	1105.6	1140.6	1175.6	1229.3	1271.3	1295.8	1308.6	1295.8
125°	790.7	902.7	1003.0	1083.5	1115.6	1147.6	1194.3	1228.1	1250.3	1257.3	1250.3
127.5°	776.8	884.1	980.9	1061.3	1091.6	1122.0	1168.6	1199.0	1217.6	1224.6	1217.6
130°	763.9	860.7	952.9	1032.2	1063.1	1094.0	1141.8	1171.0	1189.6	1196.6	1189.6
132.5°	752.3	836.2	921.4	998.3	1029.2	1060.2	1106.8	1140.6	1158.1	1165.1	1158.1
135°	740.6	814.1	889.9	961.0	990.2	1019.3	1066.0	1098.7	1117.3	1124.3	1117.3
137.5°	730.1	793.1	859.6	921.4	948.2	975.0	1019.3	1053.2	1068.3	1076.5	1068.3
140°	721.9	775.6	830.4	882.9	907.4	931.9	972.7	998.3	1014.7	1024.0	1014.7
142.5°	714.9	759.3	805.9	849.1	869.5	889.9	924.9	948.2	962.2	968.0	962.2
145°	706.8	744.1	783.8	818.7	835.0	851.4	880.6	900.4	912.0	917.9	912.0
147.5°	699.8	731.3	763.9	793.1	806.5	819.9	842.1	859.6	868.9	871.2	868.9
150°	691.6	719.6	746.4	769.8	780.2	790.7	809.4	824.6	831.6	832.7	831.6
152.5°	682.3	706.8	728.9	749.9	758.1	766.3	781.4	793.1	796.6	797.7	796.6
155°	673.0	693.9	712.6	730.1	737.1	744.1	755.8	765.1	768.6	768.6	768.6
157.5°	663.6	680.0	696.3	711.4	717.2	723.1	732.4	739.4	741.8	741.8	741.8
160°	653.1	667.1	680.0	692.8	697.4	702.1	709.1	716.1	717.3	717.3	717.3
162.5°	643.8	654.3	664.8	674.1	678.2	682.3	686.9	693.9	695.1	693.9	695.1
165°	633.3	642.6	649.6	657.8	660.7	663.6	668.3	673.0	671.8	670.6	671.8
167.5°	624.0	631.0	636.8	643.8	645.6	647.3	649.6	653.1	653.1	652.0	653.1
170°	614.6	620.5	624.0	628.6	630.4	632.1	634.5	635.6	634.5	634.5	634.5
172.5°	606.5	611.1	613.5	615.8	617.0	618.1	619.3	620.5	619.3	617.0	619.3
175°	600.6	603.0	604.1	606.5	606.5	606.5	606.5	608.8	606.5	604.1	606.5
177.5°	596.0	597.1	598.3	598.3	598.9	599.5	598.3	599.5	597.1	594.8	597.1
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4
2.5°	617.4	614.2	613.7	613.7	608.6	611.4	605.9	599.9	597.1	597.1	592.0
5°	668.8	665.6	662.3	657.2	657.2	654.5	645.7	636.9	630.4	624.8	618.8
7.5°	721.6	718.3	709.1	704.0	706.8	701.2	689.6	674.8	663.7	654.9	642.4
10°	779.0	770.2	765.5	762.8	753.1	747.0	733.6	711.9	698.0	686.4	670.2
12.5°	825.7	828.5	810.9	812.3	802.6	794.2	773.4	752.6	731.8	715.6	691.5
15°	876.2	867.8	857.2	848.9	845.6	835.4	817.9	790.1	767.4	741.9	714.6
17.5°	916.0	909.5	899.3	891.4	884.5	860.0	845.2	820.6	789.6	764.6	731.3
20°	949.8	943.7	929.4	924.3	911.8	894.2	872.9	835.0	807.2	779.9	747.5
22.5°	964.1	958.1	945.6	939.1	931.2	914.1	893.8	857.7	823.4	789.2	754.9
25°	952.1	952.1	946.1	943.7	936.8	921.5	900.7	870.2	833.6	796.6	755.8
27.5°	893.8	905.3	909.5	911.8	911.8	912.3	897.9	868.3	832.7	796.6	754.0
30°	809.5	829.0	846.1	851.2	860.0	869.7	875.7	861.4	829.4	791.5	748.9
32.5°	703.5	728.5	760.5	768.3	780.4	809.5	825.7	831.7	814.1	780.8	735.5
35°	598.0	629.5	648.9	673.0	684.1	727.1	763.2	785.0	780.8	760.9	719.7
37.5°	505.9	523.9	547.5	573.0	595.2	636.4	681.3	723.4	740.6	730.8	699.8
40°	417.5	438.8	467.0	487.8	503.1	544.3	599.9	645.7	683.2	689.2	670.2
42.5°	355.0	376.3	393.4	416.1	428.1	467.9	517.0	574.4	618.8	642.4	634.1
45°	306.9	319.8	333.7	346.7	361.5	396.7	442.0	505.0	555.0	588.3	591.5
47.5°	264.7	276.3	288.4	300.4	308.7	336.0	377.7	429.1	483.7	529.5	547.5
50°	235.1	240.7	249.5	256.4	266.1	289.7	323.1	367.5	425.4	474.9	498.5
52.5°	206.0	212.9	219.9	225.9	232.3	249.0	279.6	318.0	368.0	418.9	448.0
55°	181.4	187.0	193.5	197.6	201.3	216.1	239.3	268.9	312.0	360.1	396.2
57.5°	161.5	163.8	169.4	171.7	175.9	187.9	204.6	231.0	265.7	312.4	342.0
60°	139.8	144.4	148.6	150.4	153.7	162.0	173.6	198.1	228.2	262.4	296.2
62.5°	122.2	124.0	127.3	129.6	131.9	140.7	150.4	168.9	191.6	220.3	251.3
65°	106.0	106.9	108.8	112.0	113.4	119.9	125.4	138.9	160.1	181.9	212.9
67.5°	89.3	90.3	92.6	94.4	95.8	100.0	106.0	115.7	127.3	151.4	168.5
70°	76.4	76.4	77.8	78.7	80.1	81.9	85.2	92.6	103.2	118.5	134.2
72.5°	63.9	63.9	63.9	65.3	65.3	66.7	68.5	73.6	81.0	93.0	103.2
75°	49.5	50.0	50.9	50.9	51.4	53.2	54.6	56.0	59.7	67.6	76.8
77.5°	37.5	38.4	38.9	38.0	38.9	38.9	40.7	42.6	44.4	46.7	53.7
80°	27.8	28.2	27.3	27.8	27.8	28.7	29.6	29.2	30.1	32.9	34.7
82.5°	18.5	19.0	19.0	19.0	19.0	20.4	20.4	19.9	20.4	20.8	21.3
85°	11.6	11.1	11.1	11.6	11.1	11.1	11.6	12.0	11.6	12.0	12.5
87.5°	5.1	5.1	5.1	5.1	4.6	4.6	5.1	4.6	5.1	4.6	4.2
90°	25.7	24.5	23.3	23.3	23.3	22.2	21.0	19.8	21.0	18.7	16.3
92.5°	110.8	119.0	136.5	151.0	165.6	209.9	281.1	380.2	457.2	400.0	290.4
95°	320.7	356.9	414.0	470.6	527.2	683.4	864.2	977.4	950.5	717.3	438.5
97.5°	746.4	816.4	895.7	961.0	1026.3	1154.6	1244.4	1225.8	1017.0	686.9	400.0
100°	1113.8	1185.0	1286.4	1329.6	1372.7	1429.9	1406.6	1236.3	937.7	608.8	370.9
102.5°	1449.7	1496.4	1548.8	1560.5	1572.2	1537.2	1398.4	1148.8	838.6	556.3	362.7
105°	1664.3	1673.6	1671.3	1647.4	1623.5	1508.0	1306.3	1039.2	765.1	530.7	367.4
107.5°	1742.4	1721.5	1670.1	1621.2	1572.2	1411.2	1193.1	949.4	717.3	523.7	381.4
110°	1723.8	1674.8	1592.0	1527.8	1463.7	1294.6	1092.8	885.2	695.1	526.0	397.7

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1636.3	1574.5	1477.7	1413.6	1349.4	1192.0	1019.3	849.1	684.6	533.0	415.2
115°	1529.0	1459.0	1366.9	1310.9	1254.9	1118.5	975.0	829.2	682.3	542.3	433.9
117.5°	1421.7	1361.1	1279.4	1230.4	1181.5	1070.7	949.4	818.7	681.1	551.7	452.5
120°	1335.4	1284.1	1217.6	1176.2	1134.8	1041.5	933.0	810.6	681.1	562.2	472.3
122.5°	1271.3	1229.3	1175.6	1140.6	1105.6	1022.8	919.0	801.2	680.0	572.7	491.0
125°	1228.1	1194.3	1147.6	1115.6	1083.5	1003.0	902.7	790.7	678.8	583.1	509.7
127.5°	1199.0	1168.6	1122.0	1091.6	1061.3	980.9	884.1	776.8	676.5	591.3	526.0
130°	1171.0	1141.8	1094.0	1063.1	1032.2	952.9	860.7	763.9	675.3	600.6	541.2
132.5°	1140.6	1106.8	1060.2	1029.2	998.3	921.4	836.2	752.3	674.1	608.8	556.3
135°	1098.7	1066.0	1019.3	990.2	961.0	889.9	814.1	740.6	673.0	617.0	569.2
137.5°	1053.2	1019.3	975.0	948.2	921.4	859.6	793.1	730.1	673.0	621.6	578.5
140°	998.3	972.7	931.9	907.4	882.9	830.4	775.6	721.9	671.8	627.5	587.8
142.5°	948.2	924.9	889.9	869.5	849.1	805.9	759.3	714.9	671.8	632.1	594.8
145°	900.4	880.6	851.4	835.0	818.7	783.8	744.1	706.8	669.5	633.3	599.5
147.5°	859.6	842.1	819.9	806.5	793.1	763.9	731.3	699.8	666.0	634.5	604.1
150°	824.6	809.4	790.7	780.2	769.8	746.4	719.6	691.6	662.5	634.5	607.6
152.5°	793.1	781.4	766.3	758.1	749.9	728.9	706.8	682.3	656.6	632.1	610.0
155°	765.1	755.8	744.1	737.1	730.1	712.6	693.9	673.0	650.8	629.8	611.1
157.5°	739.4	732.4	723.1	717.2	711.4	696.3	680.0	663.6	645.0	627.5	611.1
160°	716.1	709.1	702.1	697.4	692.8	680.0	667.1	653.1	638.0	624.0	611.1
162.5°	693.9	686.9	682.3	678.2	674.1	664.8	654.3	643.8	631.0	620.5	611.1
165°	673.0	668.3	663.6	660.7	657.8	649.6	642.6	633.3	624.0	615.8	608.8
167.5°	653.1	649.6	647.3	645.6	643.8	636.8	631.0	624.0	617.0	611.1	606.5
170°	635.6	634.5	632.1	630.4	628.6	624.0	620.5	614.6	610.0	606.5	604.1
172.5°	620.5	619.3	618.1	617.0	615.8	613.5	611.1	606.5	603.0	601.8	601.8
175°	608.8	606.5	606.5	606.5	606.5	604.1	603.0	600.6	598.3	598.3	599.5
177.5°	599.5	598.3	599.5	598.9	598.3	598.3	597.1	596.0	594.8	594.8	597.1
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4
2.5°	589.2	586.9	585.5	585.0	580.9	578.6	577.2	576.2	574.9	571.2	567.9
5°	611.4	604.9	601.7	598.0	591.5	584.1	578.1	574.4	569.8	562.4	555.4
7.5°	632.2	622.5	616.1	611.0	599.9	587.8	578.1	570.2	561.4	551.3	541.5
10°	654.0	638.3	629.9	622.1	605.9	590.1	576.2	564.7	552.2	538.8	528.1
12.5°	671.1	650.3	641.0	629.9	610.0	591.5	573.9	558.2	542.0	527.6	512.4
15°	691.0	665.1	654.5	640.1	612.8	588.7	566.1	548.9	532.3	511.0	494.8
17.5°	702.6	672.5	657.2	644.7	615.1	586.0	559.6	538.3	518.9	497.6	480.4
20°	714.2	679.9	662.8	645.2	610.0	579.0	551.3	525.8	505.4	482.3	464.7
22.5°	717.9	678.1	660.0	643.8	606.8	572.1	540.1	514.2	490.6	467.5	447.6
25°	717.9	677.6	656.3	635.5	596.6	561.0	529.0	500.8	474.4	451.3	431.4
27.5°	710.5	668.4	646.1	627.2	586.9	548.5	515.6	484.6	459.1	436.0	413.3
30°	701.2	654.9	632.7	610.0	571.2	534.6	498.9	470.3	443.4	417.0	396.7
32.5°	689.6	640.6	616.1	592.9	551.7	513.8	480.9	452.7	427.2	399.9	377.2
35°	673.0	619.3	592.0	571.6	531.8	492.5	461.0	433.2	408.7	380.5	355.9
37.5°	651.7	599.9	572.1	547.1	505.9	469.8	440.2	413.3	389.3	363.3	336.0
40°	626.7	572.5	548.5	522.1	478.6	444.3	416.6	392.5	368.4	343.9	317.5
42.5°	598.5	544.8	517.9	492.5	450.8	417.0	391.1	369.4	347.1	324.5	296.2
45°	564.7	514.2	488.3	464.2	424.0	389.3	365.6	344.8	325.8	302.7	277.7
47.5°	526.7	482.7	456.4	430.4	391.1	361.0	337.9	320.3	304.1	280.9	258.3
50°	489.7	446.2	424.9	398.5	362.4	334.2	310.6	295.8	283.3	260.6	240.2
52.5°	442.9	410.1	389.7	367.0	332.3	303.6	285.1	272.2	257.3	239.8	221.7
55°	401.8	371.2	355.0	333.7	299.5	274.0	258.3	246.2	234.7	218.9	204.6
57.5°	355.0	336.0	319.8	301.3	267.5	245.8	231.9	221.7	211.1	198.1	186.5
60°	305.9	297.1	281.4	266.6	237.9	218.9	207.4	198.1	187.9	177.3	167.6
62.5°	262.4	257.3	248.1	236.5	209.7	193.5	181.9	175.0	167.6	157.8	148.6
65°	221.2	218.9	210.1	201.8	183.3	168.9	158.8	154.6	146.3	138.9	130.5
67.5°	184.7	181.9	176.8	173.1	157.4	143.9	138.9	133.3	126.4	120.8	113.9
70°	147.6	147.2	143.9	139.3	131.0	121.3	116.2	112.5	105.5	101.4	96.3
72.5°	114.8	117.1	114.3	112.5	106.9	100.0	95.3	93.0	87.5	84.2	80.5
75°	85.6	87.5	88.9	85.6	84.2	81.0	76.8	74.5	71.7	67.1	65.7
77.5°	58.3	62.5	62.5	63.4	63.9	62.0	58.8	56.9	53.7	52.8	50.9
80°	38.4	42.1	42.6	43.5	44.9	44.9	42.6	42.1	38.9	38.4	37.0
82.5°	22.2	25.5	27.3	28.7	28.2	30.1	28.2	27.8	25.9	25.9	25.0
85°	12.0	12.5	13.4	14.3	15.3	16.2	16.2	15.7	15.3	14.8	13.9
87.5°	4.6	4.6	5.1	4.6	5.1	6.0	6.5	6.5	6.0	5.6	4.6
90°	16.3	9.3	9.3	9.3	8.2	7.0	3.5	1.2	3.5	7.0	8.2
92.5°	177.3	105.0	89.8	74.6	53.6	36.2	23.3	16.3	23.3	36.2	53.6
95°	247.3	145.8	121.3	96.8	68.8	53.6	42.0	38.5	42.0	53.6	68.8
97.5°	235.6	155.1	134.1	113.1	88.6	74.6	64.1	64.1	64.1	74.6	88.6
100°	239.1	170.3	151.6	133.0	110.8	96.8	88.6	88.6	88.6	96.8	110.8
102.5°	250.8	190.1	172.6	155.1	134.1	121.3	114.3	112.0	114.3	121.3	134.1
105°	270.6	214.6	197.7	180.8	159.8	145.8	140.0	136.5	140.0	145.8	159.8
107.5°	291.6	240.3	223.4	206.4	186.6	171.4	165.6	163.3	165.6	171.4	186.6
110°	316.1	264.7	249.0	233.3	212.3	198.3	192.4	190.1	192.4	198.3	212.3

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	339.4	290.4	274.6	258.9	237.9	225.1	218.1	215.8	218.1	225.1	237.9
115°	363.9	317.2	301.4	285.7	263.6	251.9	243.8	240.3	243.8	251.9	263.6
117.5°	387.2	342.9	326.5	310.2	289.2	276.4	269.4	265.9	269.4	276.4	289.2
120°	411.7	367.4	351.0	334.7	314.9	302.1	293.9	291.6	293.9	302.1	314.9
122.5°	435.0	390.7	375.0	359.2	337.1	325.4	317.2	314.9	317.2	325.4	337.1
125°	456.0	414.0	397.7	381.4	359.2	346.4	339.4	334.7	339.4	346.4	359.2
127.5°	475.8	435.0	418.7	402.4	379.0	365.1	356.9	353.4	356.9	365.1	379.0
130°	495.7	456.0	439.1	422.2	400.0	382.5	373.2	368.5	373.2	382.5	400.0
132.5°	512.0	472.3	456.6	440.9	416.4	400.0	387.2	383.7	387.2	400.0	416.4
135°	527.2	488.7	473.6	458.4	433.9	414.0	402.4	397.7	402.4	414.0	433.9
137.5°	538.8	502.7	488.1	473.5	447.9	429.2	416.4	411.7	416.4	429.2	447.9
140°	550.5	515.5	501.5	487.5	463.0	443.2	430.4	426.9	430.4	443.2	463.0
142.5°	561.0	527.2	513.8	500.3	477.0	458.4	446.7	443.2	446.7	458.4	477.0
145°	568.0	537.7	524.8	512.0	489.8	473.5	461.9	458.4	461.9	473.5	489.8
147.5°	576.2	547.0	535.4	523.7	505.0	487.5	477.0	475.8	477.0	487.5	505.0
150°	582.0	556.3	545.2	534.2	516.7	502.7	493.3	492.2	493.3	502.7	516.7
152.5°	586.6	564.5	554.6	544.7	529.5	516.7	507.3	507.3	507.3	516.7	529.5
155°	591.3	571.5	562.8	554.0	541.2	529.5	522.5	521.3	522.5	529.5	541.2
157.5°	594.8	577.3	570.3	563.3	551.7	542.3	535.3	535.3	535.3	542.3	551.7
160°	597.1	583.1	576.7	570.3	561.0	552.8	548.2	548.2	548.2	552.8	561.0
162.5°	599.5	586.6	582.0	577.3	569.2	562.2	558.7	559.8	558.7	562.2	569.2
165°	599.5	589.0	585.5	582.0	576.2	570.3	568.0	568.0	568.0	570.3	576.2
167.5°	599.5	591.3	588.4	585.5	582.0	577.3	576.2	577.3	576.2	577.3	582.0
170°	598.3	592.5	590.8	589.0	586.6	583.1	582.0	583.1	582.0	583.1	586.6
172.5°	597.1	593.6	592.4	591.3	590.1	587.8	587.8	589.0	587.8	587.8	590.1
175°	596.0	593.6	593.6	593.6	592.5	591.3	591.3	592.5	591.3	591.3	592.5
177.5°	594.8	593.6	593.6	593.6	593.6	592.5	593.6	594.8	593.6	592.5	593.6
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4
2.5°	565.1	564.2	563.3	559.6	556.3	550.8	546.2	544.3	543.8	544.3	542.9
5°	548.9	548.5	545.2	538.8	532.7	526.3	521.6	517.0	514.2	514.2	511.0
7.5°	533.7	530.4	527.6	519.3	512.4	503.6	496.6	492.5	490.2	485.1	485.1
10°	517.5	512.8	509.1	501.3	491.1	482.3	473.5	468.4	464.2	460.5	459.1
12.5°	501.3	497.6	490.6	482.3	472.1	461.0	451.7	448.0	438.3	430.4	430.9
15°	486.0	477.7	474.4	462.4	450.4	439.7	426.3	415.6	407.8	402.7	396.2
17.5°	468.9	460.5	454.5	444.3	428.6	411.9	399.0	384.6	376.8	368.0	363.8
20°	449.9	442.9	438.3	422.1	403.1	383.2	368.9	360.1	351.3	344.8	341.1
22.5°	433.7	424.9	419.3	397.6	376.8	356.9	345.7	338.3	330.9	325.4	323.5
25°	412.9	407.8	394.3	375.4	349.9	336.5	326.8	317.1	312.9	309.2	305.0
27.5°	395.7	383.2	374.0	349.0	333.3	318.0	308.3	300.9	295.8	292.1	288.8
30°	374.4	362.9	349.9	329.1	314.7	300.4	291.6	285.6	280.0	277.7	274.9
32.5°	352.2	341.6	329.1	312.4	294.8	283.7	276.8	270.3	266.6	264.3	261.0
35°	332.3	318.9	310.6	294.8	280.5	268.0	261.5	256.0	251.8	250.9	250.4
37.5°	311.0	300.9	293.0	276.8	264.7	254.1	248.1	242.1	239.8	239.3	237.4
40°	292.5	283.7	276.3	261.0	248.1	238.4	233.7	230.0	227.7	227.7	227.3
42.5°	276.3	267.1	259.7	245.8	234.2	225.4	220.3	216.6	215.7	216.1	215.7
45°	258.3	250.4	243.0	228.6	218.9	212.4	206.9	205.0	203.7	204.1	204.6
47.5°	241.1	234.7	227.3	215.7	204.6	197.6	194.4	192.5	192.5	192.5	193.5
50°	225.9	218.5	212.0	200.0	189.8	184.2	181.4	179.1	179.6	180.0	180.5
52.5°	207.8	201.3	196.7	184.7	177.3	170.3	167.1	167.6	167.1	167.1	168.0
55°	192.1	185.6	181.0	169.9	162.5	157.8	155.1	153.7	154.1	153.2	155.1
57.5°	174.5	168.9	165.7	155.1	148.6	144.4	142.1	139.8	140.7	140.2	139.8
60°	159.2	152.7	147.6	140.2	134.7	129.6	128.2	125.9	126.8	125.9	125.4
62.5°	141.6	136.5	132.8	125.4	120.8	116.6	113.4	112.0	111.5	110.2	108.8
65°	124.0	121.3	117.6	110.2	105.5	102.3	100.4	99.0	98.6	94.9	90.7
67.5°	107.8	106.0	102.3	96.7	92.6	89.3	86.6	84.2	81.5	78.7	76.4
70°	92.6	89.8	87.5	82.4	78.7	75.4	72.7	69.9	68.5	65.7	64.8
72.5°	77.8	75.0	72.7	68.0	64.8	61.6	60.6	57.4	56.0	55.5	55.5
75°	62.5	60.2	58.8	54.6	51.8	49.5	48.1	47.2	46.3	45.4	44.0
77.5°	47.7	46.3	45.4	42.6	40.3	38.9	38.4	35.2	34.3	33.3	32.4
80°	34.7	34.3	33.3	31.0	30.1	26.8	26.8	25.9	25.5	25.5	25.5
82.5°	23.6	22.7	22.2	19.9	19.4	19.0	18.5	18.1	18.5	18.1	18.5
85°	12.5	12.0	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.1	11.6
87.5°	4.6	4.6	4.6	4.6	4.2	4.6	4.6	4.2	4.6	4.6	4.6
90°	9.3	9.3	9.3	16.3	16.3	18.7	21.0	19.8	21.0	22.2	23.3
92.5°	74.6	89.8	105.0	177.3	290.4	400.0	457.2	380.2	281.1	209.9	165.6
95°	96.8	121.3	145.8	247.3	438.5	717.3	950.5	977.4	864.2	683.4	527.2
97.5°	113.1	134.1	155.1	235.6	400.0	686.9	1017.0	1225.8	1244.4	1154.6	1026.3
100°	133.0	151.6	170.3	239.1	370.9	608.8	937.7	1236.3	1406.6	1429.9	1372.7
102.5°	155.1	172.6	190.1	250.8	362.7	556.3	838.6	1148.8	1398.4	1537.2	1572.2
105°	180.8	197.7	214.6	270.6	367.4	530.7	765.1	1039.2	1306.3	1508.0	1623.5
107.5°	206.4	223.4	240.3	291.6	381.4	523.7	717.3	949.4	1193.1	1411.2	1572.2
110°	233.3	249.0	264.7	316.1	397.7	526.0	695.1	885.2	1092.8	1294.6	1463.7

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	258.9	274.6	290.4	339.4	415.2	533.0	684.6	849.1	1019.3	1192.0	1349.4
115°	285.7	301.4	317.2	363.9	433.9	542.3	682.3	829.2	975.0	1118.5	1254.9
117.5°	310.2	326.5	342.9	387.2	452.5	551.7	681.1	818.7	949.4	1070.7	1181.5
120°	334.7	351.0	367.4	411.7	472.3	562.2	681.1	810.6	933.0	1041.5	1134.8
122.5°	359.2	375.0	390.7	435.0	491.0	572.7	680.0	801.2	919.0	1022.8	1105.6
125°	381.4	397.7	414.0	456.0	509.7	583.1	678.8	790.7	902.7	1003.0	1083.5
127.5°	402.4	418.7	435.0	475.8	526.0	591.3	676.5	776.8	884.1	980.9	1061.3
130°	422.2	439.1	456.0	495.7	541.2	600.6	675.3	763.9	860.7	952.9	1032.2
132.5°	440.9	456.6	472.3	512.0	556.3	608.8	674.1	752.3	836.2	921.4	998.3
135°	458.4	473.6	488.7	527.2	569.2	617.0	673.0	740.6	814.1	889.9	961.0
137.5°	473.5	488.1	502.7	538.8	578.5	621.6	673.0	730.1	793.1	859.6	921.4
140°	487.5	501.5	515.5	550.5	587.8	627.5	671.8	721.9	775.6	830.4	882.9
142.5°	500.3	513.8	527.2	561.0	594.8	632.1	671.8	714.9	759.3	805.9	849.1
145°	512.0	524.8	537.7	568.0	599.5	633.3	669.5	706.8	744.1	783.8	818.7
147.5°	523.7	535.4	547.0	576.2	604.1	634.5	666.0	699.8	731.3	763.9	793.1
150°	534.2	545.2	556.3	582.0	607.6	634.5	662.5	691.6	719.6	746.4	769.8
152.5°	544.7	554.6	564.5	586.6	610.0	632.1	656.6	682.3	706.8	728.9	749.9
155°	554.0	562.8	571.5	591.3	611.1	629.8	650.8	673.0	693.9	712.6	730.1
157.5°	563.3	570.3	577.3	594.8	611.1	627.5	645.0	663.6	680.0	696.3	711.4
160°	570.3	576.7	583.1	597.1	611.1	624.0	638.0	653.1	667.1	680.0	692.8
162.5°	577.3	582.0	586.6	599.5	611.1	620.5	631.0	643.8	654.3	664.8	674.1
165°	582.0	585.5	589.0	599.5	608.8	615.8	624.0	633.3	642.6	649.6	657.8
167.5°	585.5	588.4	591.3	599.5	606.5	611.1	617.0	624.0	631.0	636.8	643.8
170°	589.0	590.8	592.5	598.3	604.1	606.5	610.0	614.6	620.5	624.0	628.6
172.5°	591.3	592.4	593.6	597.1	601.8	601.8	603.0	606.5	611.1	613.5	615.8
175°	593.6	593.6	593.6	596.0	599.5	598.3	598.3	600.6	603.0	604.1	606.5
177.5°	593.6	593.6	593.6	594.8	597.1	594.8	594.8	596.0	597.1	598.3	598.3
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4
2.5°	542.9	544.8	542.5	543.8	540.6	540.1	540.6	540.6	541.1	541.5	542.0
5°	512.4	511.9	509.1	507.3	505.9	507.3	508.2	509.1	508.2	509.1	509.6
7.5°	483.7	482.3	480.9	477.7	478.6	477.7	480.4	479.0	479.0	481.4	483.2
10°	458.2	455.4	454.5	450.8	448.0	447.6	450.8	452.2	453.6	454.5	458.2
12.5°	425.4	421.2	418.0	419.3	411.5	414.7	415.6	413.8	419.3	425.8	422.1
15°	390.2	390.6	384.2	381.8	375.4	377.2	377.7	382.3	386.9	386.5	392.0
17.5°	364.3	361.5	355.9	355.5	352.7	354.1	353.6	357.3	355.9	358.2	362.9
20°	340.2	338.3	333.7	331.9	332.8	331.9	332.3	332.8	334.2	339.3	338.3
22.5°	321.2	318.9	318.9	316.6	313.8	312.9	315.2	316.6	318.4	319.4	321.7
25°	304.6	302.7	300.4	299.0	296.7	297.1	298.5	300.4	301.8	303.6	305.5
27.5°	287.4	287.4	285.1	284.7	283.7	283.3	285.1	286.0	286.0	287.4	289.3
30°	274.0	274.0	271.7	271.2	270.8	270.8	272.2	272.6	273.1	274.5	275.4
32.5°	261.0	260.6	259.7	260.1	259.7	260.1	260.1	260.6	261.5	262.0	263.8
35°	249.0	249.5	248.5	248.5	248.1	248.5	249.5	249.9	250.4	251.3	251.3
37.5°	237.4	238.4	237.9	239.3	239.3	239.3	239.3	240.2	240.2	240.2	239.8
40°	227.3	227.3	226.8	227.7	228.6	228.6	229.1	229.1	229.6	229.6	229.1
42.5°	215.7	216.6	218.0	218.5	219.4	218.9	220.3	219.9	220.3	219.4	218.5
45°	205.0	205.0	206.9	208.7	209.2	209.2	209.2	210.1	209.2	207.8	207.4
47.5°	193.5	194.4	195.3	197.6	198.1	198.1	198.1	198.1	197.2	197.2	197.2
50°	181.9	182.4	182.8	183.8	185.1	184.7	184.7	184.7	186.5	184.7	185.1
52.5°	168.0	168.5	168.9	170.8	170.3	170.3	170.8	170.8	172.2	171.7	170.8
55°	154.1	154.1	155.1	155.1	155.1	156.0	156.4	157.4	156.9	157.4	157.8
57.5°	140.2	139.3	138.9	138.9	140.2	139.8	140.2	140.2	142.1	143.0	143.5
60°	124.0	124.0	123.6	120.8	120.8	120.3	121.7	122.7	123.6	127.7	127.3
62.5°	107.4	105.5	103.7	104.1	101.4	102.8	101.8	102.8	105.5	108.8	109.2
65°	90.7	89.3	87.5	87.0	86.1	87.5	87.0	87.5	88.9	90.7	93.0
67.5°	75.9	75.4	74.5	74.1	74.1	74.1	75.0	75.0	75.4	76.8	78.2
70°	64.8	64.3	64.8	63.9	64.3	63.9	64.3	64.8	65.3	65.7	67.1
72.5°	54.6	54.6	54.6	53.7	54.6	54.2	54.2	54.6	55.1	55.5	56.5
75°	43.5	42.6	41.7	40.7	40.3	41.2	41.7	41.2	42.6	44.4	44.4
77.5°	32.9	32.4	32.4	32.4	32.9	32.4	33.3	32.9	33.3	33.3	34.3
80°	25.5	25.0	25.5	25.5	25.0	25.9	25.5	25.5	25.9	26.4	25.9
82.5°	18.5	19.0	18.5	18.5	18.5	19.4	18.5	18.5	18.5	19.0	19.0
85°	11.6	11.6	11.6	11.6	12.0	11.6	12.0	11.6	12.5	12.0	12.0
87.5°	4.2	4.6	5.1	5.1	5.1	5.1	4.6	5.1	5.6	5.1	5.6
90°	23.3	23.3	24.5	25.7	24.5	24.5	24.5	25.7	24.5	23.3	23.3
92.5°	151.0	136.5	119.0	110.8	106.1	106.1	106.1	110.8	119.0	136.5	151.0
95°	470.6	414.0	356.9	320.7	299.7	284.6	299.7	320.7	356.9	414.0	470.6
97.5°	961.0	895.7	816.4	746.4	711.4	683.4	711.4	746.4	816.4	895.7	961.0
100°	1329.6	1286.4	1185.0	1113.8	1078.8	1069.5	1078.8	1113.8	1185.0	1286.4	1329.6
102.5°	1560.5	1548.8	1496.4	1449.7	1412.4	1405.4	1412.4	1449.7	1496.4	1548.8	1560.5
105°	1647.4	1671.3	1673.6	1664.3	1648.0	1641.0	1648.0	1664.3	1673.6	1671.3	1647.4
107.5°	1621.2	1670.1	1721.5	1742.4	1751.8	1752.9	1751.8	1742.4	1721.5	1670.1	1621.2
110°	1527.8	1592.0	1674.8	1723.8	1744.8	1755.3	1744.8	1723.8	1674.8	1592.0	1527.8

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1413.6	1477.7	1574.5	1636.3	1667.8	1686.5	1667.8	1636.3	1574.5	1477.7	1413.6
115°	1310.9	1366.9	1459.0	1529.0	1566.3	1575.7	1566.3	1529.0	1459.0	1366.9	1310.9
117.5°	1230.4	1279.4	1361.1	1421.7	1461.4	1467.2	1461.4	1421.7	1361.1	1279.4	1230.4
120°	1176.2	1217.6	1284.1	1335.4	1365.7	1378.6	1365.7	1335.4	1284.1	1217.6	1176.2
122.5°	1140.6	1175.6	1229.3	1271.3	1295.8	1308.6	1295.8	1271.3	1229.3	1175.6	1140.6
125°	1115.6	1147.6	1194.3	1228.1	1250.3	1257.3	1250.3	1228.1	1194.3	1147.6	1115.6
127.5°	1091.6	1122.0	1168.6	1199.0	1217.6	1224.6	1217.6	1199.0	1168.6	1122.0	1091.6
130°	1063.1	1094.0	1141.8	1171.0	1189.6	1196.6	1189.6	1171.0	1141.8	1094.0	1063.1
132.5°	1029.2	1060.2	1106.8	1140.6	1158.1	1165.1	1158.1	1140.6	1106.8	1060.2	1029.2
135°	990.2	1019.3	1066.0	1098.7	1117.3	1124.3	1117.3	1098.7	1066.0	1019.3	990.2
137.5°	948.2	975.0	1019.3	1053.2	1068.3	1076.5	1068.3	1053.2	1019.3	975.0	948.2
140°	907.4	931.9	972.7	998.3	1014.7	1024.0	1014.7	998.3	972.7	931.9	907.4
142.5°	869.5	889.9	924.9	948.2	962.2	968.0	962.2	948.2	924.9	889.9	869.5
145°	835.0	851.4	880.6	900.4	912.0	917.9	912.0	900.4	880.6	851.4	835.0
147.5°	806.5	819.9	842.1	859.6	868.9	871.2	868.9	859.6	842.1	819.9	806.5
150°	780.2	790.7	809.4	824.6	831.6	832.7	831.6	824.6	809.4	790.7	780.2
152.5°	758.1	766.3	781.4	793.1	796.6	797.7	796.6	793.1	781.4	766.3	758.1
155°	737.1	744.1	755.8	765.1	768.6	768.6	768.6	765.1	755.8	744.1	737.1
157.5°	717.2	723.1	732.4	739.4	741.8	741.8	741.8	739.4	732.4	723.1	717.2
160°	697.4	702.1	709.1	716.1	717.3	717.3	717.3	716.1	709.1	702.1	697.4
162.5°	678.2	682.3	686.9	693.9	695.1	693.9	695.1	693.9	686.9	682.3	678.2
165°	660.7	663.6	668.3	673.0	671.8	670.6	671.8	673.0	668.3	663.6	660.7
167.5°	645.6	647.3	649.6	653.1	653.1	652.0	653.1	653.1	649.6	647.3	645.6
170°	630.4	632.1	634.5	635.6	634.5	634.5	634.5	635.6	634.5	632.1	630.4
172.5°	617.0	618.1	619.3	620.5	619.3	617.0	619.3	620.5	619.3	618.1	617.0
175°	606.5	606.5	606.5	608.8	606.5	604.1	606.5	608.8	606.5	606.5	606.5
177.5°	598.9	599.5	598.3	599.5	597.1	594.8	597.1	599.5	598.3	599.5	598.9
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4	574.4
2.5°	543.8	546.2	545.2	542.0	543.4	546.2	548.9	552.6	555.0	556.8	557.7
5°	511.9	516.1	515.1	515.1	517.0	521.6	526.3	534.1	536.9	540.1	544.8
7.5°	483.7	486.9	489.7	490.6	493.4	499.4	505.4	514.2	521.2	524.9	527.6
10°	458.7	461.0	465.2	467.5	470.3	477.7	486.5	495.7	502.7	509.1	512.8
12.5°	426.7	436.0	441.6	445.3	449.0	460.1	467.0	477.2	485.5	491.5	497.1
15°	391.1	402.2	405.5	419.8	429.1	437.9	448.5	460.5	468.4	475.3	482.7
17.5°	361.0	368.9	372.6	387.9	395.7	409.6	424.9	440.2	452.2	457.3	464.7
20°	342.0	346.2	353.6	358.7	367.0	383.2	399.9	418.4	436.5	441.6	449.0
22.5°	322.6	328.2	333.3	340.2	346.7	357.8	374.4	394.8	414.2	423.5	432.3
25°	305.0	310.6	313.8	321.2	327.2	338.3	349.9	370.7	393.9	401.8	415.6
27.5°	291.1	294.4	299.9	303.2	310.1	320.3	330.9	346.7	369.4	382.8	396.2
30°	277.2	279.6	284.2	288.8	293.9	300.9	312.9	328.2	349.0	360.6	374.0
32.5°	263.4	267.1	269.8	273.1	278.6	287.0	295.3	310.1	326.8	339.7	353.2
35°	251.8	253.2	256.9	260.6	264.3	271.7	280.5	294.8	309.6	319.8	331.9
37.5°	239.3	241.6	244.4	245.8	251.8	256.4	265.7	276.8	294.4	300.9	312.9
40°	229.6	229.1	231.9	234.2	237.0	244.4	249.9	262.0	275.9	286.0	293.4
42.5°	217.5	217.5	218.5	221.2	224.9	229.6	236.1	246.2	260.6	268.0	276.8
45°	207.8	206.4	206.9	208.7	211.1	215.7	222.2	231.0	245.3	251.3	260.6
47.5°	196.2	194.9	194.9	196.7	198.6	201.8	206.9	217.1	228.6	236.5	243.5
50°	183.3	183.8	183.3	184.7	185.6	188.8	194.4	202.7	213.4	219.9	227.7
52.5°	171.3	170.3	169.9	170.8	172.6	175.0	181.0	188.4	198.6	205.0	212.0
55°	156.4	157.4	157.4	157.4	160.1	161.1	165.7	173.1	183.3	188.4	194.9
57.5°	143.0	142.6	143.5	143.0	145.3	148.6	152.3	157.8	168.0	173.1	179.1
60°	128.2	128.7	129.1	129.1	131.0	134.2	138.4	143.5	151.8	156.9	162.5
62.5°	110.2	112.5	114.8	115.7	118.5	120.8	123.6	129.1	136.5	140.2	145.3
65°	93.0	96.3	99.5	101.8	103.7	106.0	109.7	114.8	120.8	124.5	129.6
67.5°	78.2	80.5	84.7	87.0	90.7	93.5	95.8	100.0	107.4	108.8	112.9
70°	67.6	68.5	70.4	72.2	76.4	78.7	81.5	85.6	91.2	94.4	96.7
72.5°	56.9	57.4	58.3	60.2	62.0	64.8	68.0	71.7	76.8	78.2	81.5
75°	45.4	48.1	48.1	49.5	50.9	52.3	55.1	58.8	62.0	64.3	66.2
77.5°	33.8	35.2	36.1	38.4	40.3	41.7	43.5	46.3	48.1	50.0	51.4
80°	26.4	26.8	27.3	27.3	28.2	30.1	31.9	33.8	36.1	37.0	38.4
82.5°	19.4	19.4	19.4	20.4	20.8	21.3	21.3	22.2	24.5	25.5	26.8
85°	12.5	12.5	12.5	12.5	13.0	13.4	13.9	14.3	14.3	14.3	15.3
87.5°	5.1	6.0	5.6	6.0	6.0	6.0	6.0	6.5	6.5	6.9	6.9
90°	23.3	22.2	21.0	19.8	21.0	18.7	16.3	16.3	9.3	9.3	9.3
92.5°	165.6	209.9	281.1	380.2	457.2	400.0	290.4	177.3	105.0	89.8	74.6
95°	527.2	683.4	864.2	977.4	950.5	717.3	438.5	247.3	145.8	121.3	96.8
97.5°	1026.3	1154.6	1244.4	1225.8	1017.0	686.9	400.0	235.6	155.1	134.1	113.1
100°	1372.7	1429.9	1406.6	1236.3	937.7	608.8	370.9	239.1	170.3	151.6	133.0
102.5°	1572.2	1537.2	1398.4	1148.8	838.6	556.3	362.7	250.8	190.1	172.6	155.1
105°	1623.5	1508.0	1306.3	1039.2	765.1	530.7	367.4	270.6	214.6	197.7	180.8
107.5°	1572.2	1411.2	1193.1	949.4	717.3	523.7	381.4	291.6	240.3	223.4	206.4
110°	1463.7	1294.6	1092.8	885.2	695.1	526.0	397.7	316.1	264.7	249.0	233.3

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1349.4	1192.0	1019.3	849.1	684.6	533.0	415.2	339.4	290.4	274.6	258.9
115°	1254.9	1118.5	975.0	829.2	682.3	542.3	433.9	363.9	317.2	301.4	285.7
117.5°	1181.5	1070.7	949.4	818.7	681.1	551.7	452.5	387.2	342.9	326.5	310.2
120°	1134.8	1041.5	933.0	810.6	681.1	562.2	472.3	411.7	367.4	351.0	334.7
122.5°	1105.6	1022.8	919.0	801.2	680.0	572.7	491.0	435.0	390.7	375.0	359.2
125°	1083.5	1003.0	902.7	790.7	678.8	583.1	509.7	456.0	414.0	397.7	381.4
127.5°	1061.3	980.9	884.1	776.8	676.5	591.3	526.0	475.8	435.0	418.7	402.4
130°	1032.2	952.9	860.7	763.9	675.3	600.6	541.2	495.7	456.0	439.1	422.2
132.5°	998.3	921.4	836.2	752.3	674.1	608.8	556.3	512.0	472.3	456.6	440.9
135°	961.0	889.9	814.1	740.6	673.0	617.0	569.2	527.2	488.7	473.6	458.4
137.5°	921.4	859.6	793.1	730.1	673.0	621.6	578.5	538.8	502.7	488.1	473.5
140°	882.9	830.4	775.6	721.9	671.8	627.5	587.8	550.5	515.5	501.5	487.5
142.5°	849.1	805.9	759.3	714.9	671.8	632.1	594.8	561.0	527.2	513.8	500.3
145°	818.7	783.8	744.1	706.8	669.5	633.3	599.5	568.0	537.7	524.8	512.0
147.5°	793.1	763.9	731.3	699.8	666.0	634.5	604.1	576.2	547.0	535.4	523.7
150°	769.8	746.4	719.6	691.6	662.5	634.5	607.6	582.0	556.3	545.2	534.2
152.5°	749.9	728.9	706.8	682.3	656.6	632.1	610.0	586.6	564.5	554.6	544.7
155°	730.1	712.6	693.9	673.0	650.8	629.8	611.1	591.3	571.5	562.8	554.0
157.5°	711.4	696.3	680.0	663.6	645.0	627.5	611.1	594.8	577.3	570.3	563.3
160°	692.8	680.0	667.1	653.1	638.0	624.0	611.1	597.1	583.1	576.7	570.3
162.5°	674.1	664.8	654.3	643.8	631.0	620.5	611.1	599.5	586.6	582.0	577.3
165°	657.8	649.6	642.6	633.3	624.0	615.8	608.8	599.5	589.0	585.5	582.0
167.5°	643.8	636.8	631.0	624.0	617.0	611.1	606.5	599.5	591.3	588.4	585.5
170°	628.6	624.0	620.5	614.6	610.0	606.5	604.1	598.3	592.5	590.8	589.0
172.5°	615.8	613.5	611.1	606.5	603.0	601.8	601.8	597.1	593.6	592.4	591.3
175°	606.5	604.1	603.0	600.6	598.3	598.3	599.5	596.0	593.6	593.6	593.6
177.5°	598.3	598.3	597.1	596.0	594.8	594.8	597.1	594.8	593.6	593.6	593.6
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	574.4	574.4	574.4	574.4
2.5°	561.4	564.2	568.8	575.3
5°	548.5	556.3	563.7	573.5
7.5°	536.9	546.2	556.3	570.2
10°	523.5	535.1	548.0	565.1
12.5°	507.7	523.9	538.8	557.3
15°	496.2	508.2	527.2	548.9
17.5°	480.0	496.2	515.1	539.7
20°	464.7	481.8	503.1	528.6
22.5°	448.5	467.9	489.2	516.5
25°	431.8	452.7	474.0	503.1
27.5°	416.6	435.5	459.6	489.2
30°	398.0	419.8	442.9	474.0
32.5°	380.0	402.7	426.3	457.3
35°	360.6	383.2	409.2	438.8
37.5°	341.6	366.6	390.2	418.9
40°	320.8	346.7	371.2	400.4
42.5°	300.4	327.2	351.8	376.8
45°	281.4	307.8	330.0	353.6
47.5°	263.4	287.0	309.6	330.9
50°	245.8	265.7	286.5	304.1
52.5°	227.3	246.2	262.9	278.6
55°	210.6	225.4	240.2	254.6
57.5°	190.7	205.5	218.5	229.6
60°	174.0	183.3	195.8	207.4
62.5°	155.1	165.7	175.4	182.8
65°	136.5	145.8	153.2	159.7
67.5°	120.8	126.4	131.9	138.9
70°	101.8	106.5	112.9	118.0
72.5°	85.6	89.3	92.6	98.6
75°	69.4	72.7	74.5	80.1
77.5°	53.7	56.9	58.3	61.6
80°	41.2	41.7	43.5	46.3
82.5°	28.2	29.2	29.6	31.9
85°	16.2	18.5	18.1	19.0
87.5°	6.9	7.4	8.3	9.3
90°	8.2	7.0	3.5	1.2
92.5°	53.6	36.2	23.3	16.3
95°	68.8	53.6	42.0	38.5
97.5°	88.6	74.6	64.1	64.1
100°	110.8	96.8	88.6	88.6
102.5°	134.1	121.3	114.3	112.0
105°	159.8	145.8	140.0	136.5
107.5°	186.6	171.4	165.6	163.3
110°	212.3	198.3	192.4	190.1

TEST NUMBER: P1026273

CATALOG NUMBER: S124RDIP-B350D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	237.9	225.1	218.1	215.8
115°	263.6	251.9	243.8	240.3
117.5°	289.2	276.4	269.4	265.9
120°	314.9	302.1	293.9	291.6
122.5°	337.1	325.4	317.2	314.9
125°	359.2	346.4	339.4	334.7
127.5°	379.0	365.1	356.9	353.4
130°	400.0	382.5	373.2	368.5
132.5°	416.4	400.0	387.2	383.7
135°	433.9	414.0	402.4	397.7
137.5°	447.9	429.2	416.4	411.7
140°	463.0	443.2	430.4	426.9
142.5°	477.0	458.4	446.7	443.2
145°	489.8	473.5	461.9	458.4
147.5°	505.0	487.5	477.0	475.8
150°	516.7	502.7	493.3	492.2
152.5°	529.5	516.7	507.3	507.3
155°	541.2	529.5	522.5	521.3
157.5°	551.7	542.3	535.3	535.3
160°	561.0	552.8	548.2	548.2
162.5°	569.2	562.2	558.7	559.8
165°	576.2	570.3	568.0	568.0
167.5°	582.0	577.3	576.2	577.3
170°	586.6	583.1	582.0	583.1
172.5°	590.1	587.8	587.8	589.0
175°	592.5	591.3	591.3	592.5
177.5°	593.6	592.5	593.6	594.8
180°	593.6	593.6	593.6	593.6

(END OF REPORT)