

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026325

Luminaire Tested: S124RDIP-B350D590UB30-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026325
REPORT IS A COMBINATION OF REPORTS P999355 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D590UB30-4F0-XX-W2A-A
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3811.0 lumens
Efficiency: N/A
Efficacy: 134.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38		
1	95	91	88	84	87	83	80	77	68	66	64	53	52	51	40	40	39	33		
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28		
3	80	71	64	58	72	64	59	54	53	49	45	42	39	37	32	30	29	24		
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21		
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18		
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16		
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17	14		
8	53	41	34	28	48	38	31	27	31	26	23	26	22	19	20	17	15	13		
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	18	16	14	12		
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4661	4661	4661	4661
5°	4661	5267	4669	4025
10°	4636	6072	4633	3501
15°	4581	6834	4581	2931
20°	4523	7409	4500	2582
25°	4453	7440	4433	2331
30°	4378	6327	4344	2160
35°	4272	4774	4218	2032
40°	4154	3459	4072	1931
45°	3959	2629	3861	1843
50°	3728	2125	3626	1713
55°	3477	1759	3363	1540
60°	3226	1488	3081	1281
65°	2910	1212	2817	1019
70°	2621	982	2496	827
75°	2297	708	2138	606
80°	1896	470	1723	446
85°	1375	241	1142	241

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 5835 cd/sqm

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.4	1.5
10°-20°	167.2	4.4
20°-30°	261.8	6.9
30°-40°	290.8	7.6
40°-50°	257.6	6.8
50°-60°	200.8	5.3
60°-70°	131.3	3.4
70°-80°	64.4	1.7
80°-90°	17.3	0.5
90°-100°	25.4	0.7
100°-110°	167.0	4.4
110°-120°	319.0	8.4
120°-130°	404.9	10.6
130°-140°	433.2	11.4
140°-150°	405.0	10.6
150°-160°	326.6	8.6
160°-170°	210.7	5.5
170°-180°	72.6	1.9
0°-30°	484.3	12.7
0°-40°	775.1	20.3
0°-60°	1233.5	32.4
0°-90°	1446.6	38.0
90°-120°	511.4	13.4
90°-150°	1754.5	46.0
90°-180°	2364.0	62.0
0°-180°	3811.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	572	572	572	572	572	
5°	571	660	572	505	571	54
15°	546	875	546	375	546	154
25°	501	944	498	296	501	231
35°	437	581	431	247	437	273
45°	352	297	343	208	352	271
55°	253	177	245	155	253	227
65°	159	104	154	87	159	158
75°	80	48	74	41	80	85
85°	19	12	16	12	19	21
90°	2	17	2	17	2	3
95°	31	17	31	17	31	39
105°	172	163	172	163	172	180
115°	321	324	321	324	321	316
125°	452	455	452	455	452	403
135°	560	564	560	564	560	432
145°	646	649	646	649	646	404
155°	708	708	708	708	708	327
165°	747	744	747	744	747	211
175°	764	760	764	760	764	73
180°	764	764	764	764	764	

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	572.5	577.6	580.4	582.7	587.3	589.1	592.8	593.7	597.4	597.0	595.6
5°	570.7	579.5	585.9	592.8	601.1	605.7	610.8	618.1	621.8	626.9	630.1
7.5°	567.5	579.5	590.0	600.6	614.0	621.4	627.8	639.3	649.0	657.3	666.5
10°	562.4	577.6	593.3	607.6	626.0	634.7	644.4	661.4	674.8	686.3	701.1
12.5°	554.6	575.8	593.3	612.6	636.1	648.1	661.0	681.3	696.9	715.8	734.2
15°	546.3	569.8	592.8	618.1	644.9	658.7	671.6	698.8	722.7	744.4	764.6
17.5°	537.1	562.9	588.2	616.3	648.5	665.6	680.8	713.5	739.7	767.8	788.1
20°	526.0	554.1	583.1	614.5	650.9	669.7	686.8	724.1	753.1	783.5	808.8
22.5°	514.0	544.4	576.2	610.3	648.1	668.8	688.6	728.7	762.3	790.4	824.5
25°	500.7	532.9	565.6	601.6	643.9	666.5	686.8	726.4	762.3	799.2	832.3
27.5°	486.9	520.0	554.1	591.9	635.2	657.3	680.3	718.6	760.5	800.6	834.2
30°	471.7	503.9	539.8	575.8	621.8	643.9	667.4	708.9	754.5	794.6	831.0
32.5°	455.1	488.3	522.3	559.6	604.8	628.7	650.4	697.4	743.9	783.5	817.6
35°	436.7	468.0	500.2	538.5	583.1	604.8	630.6	679.4	726.4	768.3	790.4
37.5°	416.9	446.8	476.7	514.5	557.3	583.6	608.9	658.2	708.0	736.1	747.6
40°	398.4	424.7	450.9	487.3	530.6	557.8	583.6	634.7	678.5	700.1	691.4
42.5°	374.9	402.1	425.6	459.2	503.0	528.3	554.6	607.6	643.0	651.8	630.1
45°	351.9	374.5	397.1	429.8	475.8	497.5	525.6	574.8	604.3	596.5	564.7
47.5°	329.3	347.8	369.0	400.7	442.2	468.0	494.2	537.1	557.8	546.8	502.5
50°	302.6	321.0	343.2	370.8	410.9	435.7	456.5	496.1	511.7	484.6	431.1
52.5°	277.3	293.4	312.3	338.1	376.3	398.9	421.5	455.5	460.6	429.3	373.1
55°	253.3	266.2	286.0	306.8	341.8	365.7	381.4	410.4	409.0	369.9	321.5
57.5°	228.5	240.4	253.8	275.4	308.6	326.6	343.6	369.0	355.6	322.4	274.5
60°	206.4	213.3	226.6	247.4	275.4	291.1	304.5	318.3	306.8	270.8	234.0
62.5°	181.9	189.8	199.4	216.0	240.9	255.6	265.3	271.3	259.3	231.7	198.1
65°	158.9	165.8	176.0	190.7	209.6	220.6	225.7	229.8	223.4	192.1	165.4
67.5°	138.2	142.8	152.0	161.7	181.9	184.7	191.6	193.5	180.6	156.6	135.4
70°	117.5	122.1	126.2	137.7	146.9	152.0	153.4	153.4	140.5	124.8	107.3
72.5°	98.1	100.9	105.0	112.9	117.9	121.6	123.4	121.1	109.2	96.3	83.4
75°	79.7	81.1	84.8	89.8	94.0	92.6	92.1	89.4	80.6	71.4	64.0
77.5°	61.3	62.2	66.3	67.7	67.7	69.1	67.2	64.5	57.1	50.2	47.0
80°	46.1	47.4	47.9	48.8	47.9	47.9	46.5	41.9	38.2	35.0	32.7
82.5°	31.8	32.7	33.2	31.8	32.7	31.3	29.0	25.8	23.5	23.0	22.1
85°	18.9	19.3	18.9	18.9	17.5	17.0	15.2	14.7	13.8	13.8	13.4
87.5°	9.2	8.8	7.8	6.9	6.9	6.4	6.9	6.0	6.9	6.4	6.0
90°	1.7	3.1	4.5	5.9	7.3	8.0	8.5	9.5	10.6	11.6	12.6
92.5°	8.6	8.3	8.1	7.8	7.5	7.4	7.9	8.9	10.0	11.0	12.0
95°	31.4	27.1	22.8	18.5	14.2	12.0	12.1	12.2	12.3	12.5	12.6
97.5°	60.0	62.8	65.6	68.4	71.2	72.6	65.9	52.6	39.3	25.9	12.6
100°	93.7	96.0	98.3	100.6	102.9	104.0	95.2	77.7	60.2	42.6	25.1
102.5°	131.4	132.9	134.5	136.0	137.5	138.3	139.1	140.6	142.1	143.7	145.2
105°	172.0	172.8	173.6	174.3	175.1	175.5	175.8	176.4	177.1	177.7	178.3
107.5°	209.2	209.6	210.0	210.3	210.7	210.9	211.3	212.2	213.1	214.0	214.9
110°	246.9	247.3	247.7	248.0	248.4	248.6	249.0	249.7	250.5	251.2	252.0

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	283.5	284.3	285.0	285.8	286.5	286.9	287.0	287.3	287.5	287.8	288.0
115°	321.2	321.6	322.0	322.3	322.7	322.9	322.8	322.7	322.6	322.4	322.3
117.5°	354.9	355.4	355.9	356.4	356.9	357.2	357.4	357.8	358.1	358.5	358.9
120°	389.2	389.7	390.2	390.7	391.2	391.5	391.4	391.3	391.2	391.0	390.9
122.5°	421.2	421.4	421.7	421.9	422.2	422.3	422.4	422.7	423.0	423.2	423.5
125°	451.5	452.0	452.5	453.0	453.5	453.8	453.7	453.4	453.1	452.9	452.6
127.5°	480.6	480.7	480.9	481.0	481.1	481.2	481.5	482.2	482.8	483.5	484.1
130°	508.6	508.7	508.9	509.0	509.1	509.2	509.4	509.8	510.1	510.5	510.9
132.5°	534.4	534.6	534.9	535.1	535.4	535.5	535.8	536.3	536.8	537.3	537.8
135°	560.1	560.0	559.8	559.7	559.6	559.5	559.8	560.3	560.8	561.3	561.8
137.5°	582.9	582.9	582.9	582.9	582.9	582.9	583.2	583.9	584.5	585.2	585.8
140°	605.2	605.5	605.7	606.0	606.3	606.4	606.5	606.8	607.0	607.3	607.5
142.5°	625.2	625.7	626.2	626.7	627.2	627.5	627.6	627.7	627.8	628.0	628.1
145°	645.8	646.2	646.6	646.9	647.3	647.5	647.5	647.5	647.5	647.5	647.5
147.5°	661.8	662.6	663.3	664.1	664.8	665.2	665.1	665.0	664.9	664.8	664.7
150°	679.5	680.0	680.5	681.0	681.5	681.8	681.7	681.6	681.5	681.3	681.2
152.5°	694.4	694.8	695.2	695.5	695.9	696.1	696.0	695.7	695.5	695.2	695.0
155°	708.1	708.2	708.4	708.5	708.6	708.7	708.5	708.1	707.8	707.4	707.0
157.5°	720.1	720.1	720.1	720.1	720.1	720.1	719.8	719.3	718.8	718.3	717.8
160°	730.4	730.0	729.6	729.3	728.9	728.7	728.6	728.5	728.4	728.2	728.1
162.5°	739.5	739.0	738.5	738.0	737.5	737.2	737.1	737.0	736.9	736.8	736.7
165°	747.0	746.4	745.7	745.1	744.4	744.1	744.1	744.1	744.1	744.1	744.1
167.5°	753.3	752.7	752.0	751.4	750.7	750.4	750.3	750.2	750.1	749.9	749.8
170°	758.4	757.6	756.9	756.1	755.4	755.0	755.1	755.2	755.3	755.4	755.5
172.5°	761.8	761.0	760.3	759.5	758.8	758.4	758.5	758.6	758.7	758.9	759.0
175°	764.1	763.3	762.6	761.8	761.1	760.7	760.8	760.9	761.0	761.2	761.3
177.5°	765.8	764.9	764.0	763.1	762.2	761.8	761.9	762.2	762.5	762.7	763.0
180°	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	599.3	604.3	604.8	609.4	608.0	605.7	609.9	607.1	612.6	610.8	613.1
5°	634.3	641.2	647.2	650.9	657.3	655.9	662.8	660.5	665.6	660.5	667.0
7.5°	675.3	686.8	692.8	702.4	705.2	705.7	714.0	715.8	719.0	715.8	719.5
10°	715.3	729.2	743.0	750.8	755.9	762.8	770.2	773.4	775.7	772.5	774.8
12.5°	751.7	773.4	788.6	804.2	807.9	813.9	821.7	820.8	830.0	828.2	832.3
15°	785.4	809.3	827.7	840.2	850.3	855.4	870.1	871.0	870.6	875.2	872.4
17.5°	815.3	835.6	861.8	877.9	890.4	890.4	898.7	915.7	914.3	913.9	916.6
20°	839.7	862.7	887.1	914.3	924.5	926.3	937.8	946.6	947.9	947.9	947.9
22.5°	858.1	885.3	911.6	930.9	938.7	945.2	955.3	960.8	962.7	961.8	962.7
25°	867.3	893.1	919.9	937.4	942.0	945.6	946.6	949.8	949.3	943.8	947.0
27.5°	869.2	894.1	911.6	916.2	913.9	911.6	896.8	898.2	894.1	885.8	889.0
30°	860.9	874.2	873.8	859.5	855.4	845.7	832.3	812.5	796.4	789.5	791.8
32.5°	831.0	831.0	814.4	782.1	767.8	750.3	726.4	708.4	687.2	682.6	691.4
35°	789.5	766.0	735.6	693.2	671.6	658.7	617.2	604.3	586.4	581.3	585.4
37.5°	725.0	685.9	641.6	602.0	583.6	560.6	524.2	505.8	492.9	484.1	488.3
40°	652.7	605.2	559.2	510.4	490.1	471.2	444.0	427.5	406.7	407.6	409.0
42.5°	583.6	527.9	476.3	431.1	411.8	396.1	377.2	357.0	349.6	347.3	345.0
45°	510.4	450.9	402.6	369.0	351.5	336.7	319.2	307.7	298.9	297.1	299.4
47.5°	441.3	391.1	345.0	313.7	299.4	292.0	278.2	267.6	262.1	257.5	260.2
50°	378.6	331.6	294.8	268.5	258.4	253.3	240.4	234.9	229.4	228.0	227.5
52.5°	327.0	287.0	255.2	234.0	226.2	223.4	213.7	205.9	201.3	202.7	203.6
55°	280.1	246.0	221.1	204.1	197.6	194.4	187.5	181.9	178.7	177.3	178.3
57.5°	238.6	209.1	191.2	177.3	172.3	170.9	163.5	161.7	159.4	158.0	158.0
60°	200.8	180.1	163.5	155.7	150.2	148.8	143.3	140.9	140.5	139.1	138.2
62.5°	169.0	152.0	140.5	132.2	129.9	129.4	125.7	123.0	121.6	120.7	120.7
65°	141.4	129.0	119.3	113.3	111.5	110.5	106.4	105.5	104.6	103.6	103.2
67.5°	117.9	106.9	100.0	95.8	93.5	94.0	91.7	89.8	89.8	89.4	88.9
70°	95.3	88.4	82.5	80.1	79.2	78.3	77.4	76.0	75.5	75.5	75.5
72.5°	75.1	70.5	67.2	65.9	64.9	64.0	63.1	63.1	63.1	62.6	62.6
75°	57.6	55.7	53.4	52.0	52.0	53.0	51.6	50.2	48.8	47.9	48.4
77.5°	43.3	42.4	41.0	38.7	39.2	38.2	38.2	37.3	37.8	37.8	36.8
80°	31.8	30.4	29.9	28.6	29.0	28.6	28.1	28.1	27.2	27.2	27.2
82.5°	22.1	20.7	20.7	20.3	19.8	19.8	19.3	19.3	19.8	18.9	18.9
85°	13.4	12.9	12.9	12.0	12.0	12.0	12.0	12.4	12.0	11.5	11.5
87.5°	6.0	6.4	6.0	5.5	5.5	5.5	5.1	5.1	4.6	5.1	5.1
90°	13.4	14.1	14.9	15.6	16.0	16.1	16.4	16.6	16.9	17.1	16.9
92.5°	12.8	13.5	14.3	15.0	15.4	15.4	15.4	15.4	15.4	15.4	15.4
95°	13.4	14.1	14.9	15.6	16.0	16.1	16.2	16.3	16.5	16.6	16.5
97.5°	13.2	13.8	14.5	15.1	15.4	15.5	15.6	15.7	15.9	16.0	15.9
100°	22.9	20.8	18.6	16.5	15.4	15.5	15.6	15.7	15.9	16.0	15.9
102.5°	116.6	88.0	59.5	30.9	16.6	16.6	16.6	16.6	16.6	16.6	16.6
105°	179.5	180.6	181.8	182.9	183.5	181.2	176.6	172.1	167.5	162.9	167.5
107.5°	215.5	216.1	216.8	217.4	217.7	218.0	218.5	219.0	219.5	220.0	219.5
110°	252.3	252.5	252.8	253.1	253.2	253.4	253.8	254.1	254.5	254.9	254.5

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	287.9	287.8	287.7	287.6	287.5	287.8	288.3	288.8	289.3	289.8	289.3
115°	322.6	322.8	323.1	323.4	323.5	323.5	323.5	323.5	323.5	323.5	323.5
117.5°	358.8	358.6	358.5	358.4	358.3	358.3	358.3	358.3	358.3	358.3	358.3
120°	391.2	391.4	391.7	392.0	392.1	392.0	391.7	391.4	391.2	390.9	391.2
122.5°	423.6	423.8	423.9	424.0	424.1	424.0	423.7	423.4	423.2	422.9	423.2
125°	453.0	453.4	453.8	454.2	454.4	454.5	454.6	454.7	454.8	454.9	454.8
127.5°	484.0	483.8	483.7	483.6	483.5	483.4	483.3	483.2	483.0	482.9	483.0
130°	511.0	511.2	511.3	511.4	511.5	511.5	511.5	511.5	511.5	511.5	511.5
132.5°	537.9	538.1	538.2	538.3	538.4	538.3	538.2	538.1	537.9	537.8	537.9
135°	562.0	562.3	562.5	562.8	562.9	563.0	563.3	563.6	563.8	564.1	563.8
137.5°	586.0	586.3	586.5	586.8	586.9	586.8	586.7	586.6	586.5	586.4	586.5
140°	607.9	608.3	608.6	609.0	609.2	609.3	609.4	609.5	609.7	609.8	609.7
142.5°	628.3	628.6	628.8	629.1	629.2	629.2	629.2	629.2	629.2	629.2	629.2
145°	647.6	647.8	647.9	648.0	648.1	648.2	648.5	648.7	649.0	649.2	649.0
147.5°	664.8	664.9	665.0	665.1	665.2	665.3	665.4	665.5	665.7	665.8	665.7
150°	681.2	681.2	681.2	681.2	681.2	681.3	681.4	681.5	681.7	681.8	681.7
152.5°	695.2	695.5	695.7	696.0	696.1	696.0	695.9	695.8	695.6	695.5	695.6
155°	707.5	708.0	708.5	709.0	709.2	709.0	708.6	708.3	707.9	707.5	707.9
157.5°	718.4	719.1	719.7	720.4	720.7	720.4	719.7	719.1	718.4	717.8	718.4
160°	728.9	729.6	730.4	731.1	731.5	731.1	730.4	729.6	728.9	728.1	728.9
162.5°	737.5	738.2	739.0	739.7	740.1	739.7	738.8	737.9	737.0	736.1	737.0
165°	745.1	746.1	747.2	748.2	748.7	748.1	747.0	745.8	744.7	743.5	744.7
167.5°	751.0	752.1	753.3	754.4	755.0	754.4	753.1	751.8	750.5	749.2	750.5
170°	756.5	757.5	758.6	759.6	760.1	759.5	758.2	756.9	755.7	754.4	755.7
172.5°	760.0	761.0	762.0	763.0	763.5	762.8	761.4	760.1	758.7	757.3	758.7
175°	762.4	763.6	764.7	765.8	766.4	765.6	764.1	762.6	761.0	759.5	761.0
177.5°	764.0	765.0	766.0	767.0	767.5	766.7	765.2	763.7	762.2	760.7	762.2
180°	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	614.5	611.2	610.8	610.8	605.7	608.5	602.9	597.0	594.2	594.2	589.1
5°	665.6	662.4	659.1	654.1	654.1	651.3	642.6	633.8	627.4	621.8	615.8
7.5°	718.1	714.9	705.7	700.6	703.4	697.8	686.3	671.6	660.5	651.8	639.3
10°	775.2	766.5	761.9	759.1	749.4	743.4	730.1	708.4	694.6	683.1	667.0
12.5°	821.7	824.5	807.0	808.4	798.7	790.4	769.7	749.0	728.2	712.1	688.2
15°	871.9	863.7	853.1	844.8	841.5	831.4	813.9	786.3	763.7	738.4	711.2
17.5°	911.6	905.1	895.0	887.1	880.2	855.8	841.1	816.7	785.8	760.9	727.8
20°	945.2	939.2	924.9	919.9	907.4	889.9	868.7	831.0	803.3	776.1	743.9
22.5°	959.5	953.5	941.0	934.6	926.8	909.7	889.4	853.5	819.4	785.4	751.3
25°	947.5	947.5	941.5	939.2	932.3	917.1	896.4	866.0	829.6	792.7	752.2
27.5°	889.4	901.0	905.1	907.4	907.4	907.9	893.6	864.1	828.6	792.7	750.3
30°	805.6	825.0	842.0	847.1	855.8	865.5	871.5	857.2	825.4	787.7	745.3
32.5°	700.1	725.0	756.8	764.6	776.6	805.6	821.7	827.7	810.2	777.1	731.9
35°	595.1	626.4	645.8	669.7	680.8	723.6	759.6	781.2	777.1	757.3	716.3
37.5°	503.5	521.4	544.9	570.2	592.4	633.3	678.0	719.9	737.0	727.3	696.5
40°	415.5	436.7	464.8	485.5	500.7	541.7	597.0	642.6	679.9	685.9	667.0
42.5°	353.3	374.5	391.5	414.1	426.1	465.7	514.5	571.6	615.8	639.3	631.0
45°	305.4	318.3	332.1	345.0	359.7	394.7	439.9	502.5	552.3	585.4	588.7
47.5°	263.5	275.0	287.0	298.9	307.2	334.4	375.9	427.0	481.3	526.9	544.9
50°	234.0	239.5	248.3	255.2	264.9	288.3	321.5	365.7	423.3	472.6	496.1
52.5°	205.0	211.9	218.8	224.8	231.2	247.8	278.2	316.4	366.2	416.9	445.9
55°	180.6	186.1	192.5	196.7	200.4	215.1	238.1	267.6	310.5	358.4	394.3
57.5°	160.8	163.1	168.6	170.9	175.0	187.0	203.6	229.8	264.4	310.9	340.4
60°	139.1	143.7	147.9	149.7	152.9	161.2	172.7	197.1	227.1	261.2	294.8
62.5°	121.6	123.4	126.7	129.0	131.3	140.0	149.7	168.1	190.7	219.3	250.1
65°	105.5	106.4	108.2	111.5	112.9	119.3	124.8	138.2	159.4	181.0	211.9
67.5°	88.9	89.8	92.1	94.0	95.3	99.5	105.5	115.2	126.7	150.6	167.7
70°	76.0	76.0	77.4	78.3	79.7	81.5	84.8	92.1	102.7	117.9	133.6
72.5°	63.6	63.6	63.6	64.9	64.9	66.3	68.2	73.2	80.6	92.6	102.7
75°	49.3	49.7	50.7	50.7	51.1	53.0	54.4	55.7	59.4	67.2	76.5
77.5°	37.3	38.2	38.7	37.8	38.7	38.7	40.5	42.4	44.2	46.5	53.4
80°	27.6	28.1	27.2	27.6	27.6	28.6	29.5	29.0	29.9	32.7	34.5
82.5°	18.4	18.9	18.9	18.9	18.9	20.3	20.3	19.8	20.3	20.7	21.2
85°	11.5	11.1	11.1	11.5	11.1	11.1	11.5	12.0	11.5	12.0	12.4
87.5°	5.1	5.1	5.1	5.1	4.6	4.6	5.1	4.6	5.1	4.6	4.1
90°	16.6	16.4	16.1	16.0	15.6	14.9	14.1	13.4	12.6	11.6	10.6
92.5°	15.4	15.4	15.4	15.4	15.0	14.3	13.5	12.8	12.0	11.0	10.0
95°	16.3	16.2	16.1	16.0	15.6	14.9	14.1	13.4	12.6	12.5	12.3
97.5°	15.7	15.6	15.5	15.4	15.1	14.5	13.8	13.2	12.6	25.9	39.3
100°	15.7	15.6	15.5	15.4	16.5	18.6	20.8	22.9	25.1	42.6	60.2
102.5°	16.6	16.6	16.6	16.6	30.9	59.5	88.0	116.6	145.2	143.7	142.1
105°	172.1	176.6	181.2	183.5	182.9	181.8	180.6	179.5	178.3	177.7	177.1
107.5°	219.0	218.5	218.0	217.7	217.4	216.8	216.1	215.5	214.9	214.0	213.1
110°	254.1	253.8	253.4	253.2	253.1	252.8	252.5	252.3	252.0	251.2	250.5

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	288.8	288.3	287.8	287.5	287.6	287.7	287.8	287.9	288.0	287.8	287.5
115°	323.5	323.5	323.5	323.5	323.4	323.1	322.8	322.6	322.3	322.4	322.6
117.5°	358.3	358.3	358.3	358.3	358.4	358.5	358.6	358.8	358.9	358.5	358.1
120°	391.4	391.7	392.0	392.1	392.0	391.7	391.4	391.2	390.9	391.0	391.2
122.5°	423.4	423.7	424.0	424.1	424.0	423.9	423.8	423.6	423.5	423.2	423.0
125°	454.7	454.6	454.5	454.4	454.2	453.8	453.4	453.0	452.6	452.9	453.1
127.5°	483.2	483.3	483.4	483.5	483.6	483.7	483.8	484.0	484.1	483.5	482.8
130°	511.5	511.5	511.5	511.5	511.4	511.3	511.2	511.0	510.9	510.5	510.1
132.5°	538.1	538.2	538.3	538.4	538.3	538.2	538.1	537.9	537.8	537.3	536.8
135°	563.6	563.3	563.0	562.9	562.8	562.5	562.3	562.0	561.8	561.3	560.8
137.5°	586.6	586.7	586.8	586.9	586.8	586.5	586.3	586.0	585.8	585.2	584.5
140°	609.5	609.4	609.3	609.2	609.0	608.6	608.3	607.9	607.5	607.3	607.0
142.5°	629.2	629.2	629.2	629.2	629.1	628.8	628.6	628.3	628.1	628.0	627.8
145°	648.7	648.5	648.2	648.1	648.0	647.9	647.8	647.6	647.5	647.5	647.5
147.5°	665.5	665.4	665.3	665.2	665.1	665.0	664.9	664.8	664.7	664.8	664.9
150°	681.5	681.4	681.3	681.2	681.2	681.2	681.2	681.2	681.2	681.3	681.5
152.5°	695.8	695.9	696.0	696.1	696.0	695.7	695.5	695.2	695.0	695.2	695.5
155°	708.3	708.6	709.0	709.2	709.0	708.5	708.0	707.5	707.0	707.4	707.8
157.5°	719.1	719.7	720.4	720.7	720.4	719.7	719.1	718.4	717.8	718.3	718.8
160°	729.6	730.4	731.1	731.5	731.1	730.4	729.6	728.9	728.1	728.2	728.4
162.5°	737.9	738.8	739.7	740.1	739.7	739.0	738.2	737.5	736.7	736.8	736.9
165°	745.8	747.0	748.1	748.7	748.2	747.2	746.1	745.1	744.1	744.1	744.1
167.5°	751.8	753.1	754.4	755.0	754.4	753.3	752.1	751.0	749.8	749.9	750.1
170°	756.9	758.2	759.5	760.1	759.6	758.6	757.5	756.5	755.5	755.4	755.3
172.5°	760.1	761.4	762.8	763.5	763.0	762.0	761.0	760.0	759.0	758.9	758.7
175°	762.6	764.1	765.6	766.4	765.8	764.7	763.6	762.4	761.3	761.2	761.0
177.5°	763.7	765.2	766.7	767.5	767.0	766.0	765.0	764.0	763.0	762.7	762.5
180°	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	586.4	584.1	582.7	582.2	578.1	575.8	574.4	573.5	572.1	568.4	565.2
5°	608.5	602.0	598.8	595.1	588.7	581.3	575.3	571.6	567.0	559.6	552.7
7.5°	629.2	619.5	613.1	608.0	597.0	585.0	575.3	567.5	558.7	548.6	538.9
10°	650.9	635.2	626.9	619.1	602.9	587.3	573.5	562.0	549.5	536.2	525.6
12.5°	667.9	647.2	638.0	626.9	607.1	588.7	571.2	555.5	539.4	525.1	509.9
15°	687.7	661.9	651.3	637.0	609.9	585.9	563.3	546.3	529.7	508.5	492.4
17.5°	699.2	669.3	654.1	641.6	612.2	583.1	556.9	535.7	516.4	495.2	478.1
20°	710.7	676.6	659.6	642.1	607.1	576.2	548.6	523.3	503.0	480.0	462.5
22.5°	714.4	674.8	656.8	640.7	603.9	569.3	537.5	511.7	488.3	465.2	445.4
25°	714.4	674.3	653.2	632.4	593.7	558.3	526.5	498.4	472.1	449.1	429.3
27.5°	707.0	665.1	643.0	624.1	584.1	545.8	513.1	482.3	456.9	433.9	411.3
30°	697.8	651.8	629.7	607.1	568.4	532.0	496.5	468.0	441.3	415.0	394.7
32.5°	686.3	637.5	613.1	590.0	549.1	511.3	478.6	450.5	425.1	398.0	375.4
35°	669.7	616.3	589.1	568.9	529.2	490.1	458.8	431.1	406.7	378.6	354.2
37.5°	648.5	597.0	569.3	544.4	503.5	467.5	438.0	411.3	387.4	361.6	334.4
40°	623.7	569.8	545.8	519.6	476.3	442.2	414.6	390.6	366.7	342.2	316.0
42.5°	595.6	542.1	515.4	490.1	448.6	415.0	389.2	367.6	345.5	322.9	294.8
45°	562.0	511.7	486.0	462.0	421.9	387.4	363.9	343.2	324.3	301.2	276.4
47.5°	524.2	480.4	454.2	428.4	389.2	359.3	336.2	318.7	302.6	279.6	257.0
50°	487.3	444.0	422.8	396.6	360.7	332.6	309.1	294.3	281.9	259.3	239.1
52.5°	440.8	408.1	387.8	365.3	330.7	302.2	283.7	270.8	256.1	238.6	220.6
55°	399.8	369.4	353.3	332.1	298.0	272.7	257.0	245.0	233.5	217.9	203.6
57.5°	353.3	334.4	318.3	299.9	266.2	244.6	230.8	220.6	210.0	197.1	185.6
60°	304.5	295.7	280.1	265.3	236.8	217.9	206.4	197.1	187.0	176.4	166.7
62.5°	261.2	256.1	246.9	235.4	208.7	192.5	181.0	174.1	166.7	157.1	147.9
65°	220.2	217.9	209.1	200.8	182.4	168.1	158.0	153.8	145.6	138.2	129.9
67.5°	183.8	181.0	176.0	172.3	156.6	143.3	138.2	132.7	125.7	120.2	113.3
70°	146.9	146.5	143.3	138.6	130.4	120.7	115.6	111.9	105.0	100.9	95.8
72.5°	114.2	116.5	113.8	111.9	106.4	99.5	94.9	92.6	87.1	83.8	80.1
75°	85.2	87.1	88.4	85.2	83.8	80.6	76.5	74.2	71.4	66.8	65.4
77.5°	58.0	62.2	62.2	63.1	63.6	61.7	58.5	56.7	53.4	52.5	50.7
80°	38.2	41.9	42.4	43.3	44.7	44.7	42.4	41.9	38.7	38.2	36.8
82.5°	22.1	25.3	27.2	28.6	28.1	29.9	28.1	27.6	25.8	25.8	24.9
85°	12.0	12.4	13.4	14.3	15.2	16.1	16.1	15.7	15.2	14.7	13.8
87.5°	4.6	4.6	5.1	4.6	5.1	6.0	6.4	6.4	6.0	5.5	4.6
90°	9.5	8.5	8.0	7.3	5.9	4.5	3.1	1.7	3.1	4.5	5.9
92.5°	8.9	7.9	7.4	7.5	7.8	8.1	8.3	8.6	8.3	8.1	7.8
95°	12.2	12.1	12.0	14.2	18.5	22.8	27.1	31.4	27.1	22.8	18.5
97.5°	52.6	65.9	72.6	71.2	68.4	65.6	62.8	60.0	62.8	65.6	68.4
100°	77.7	95.2	104.0	102.9	100.6	98.3	96.0	93.7	96.0	98.3	100.6
102.5°	140.6	139.1	138.3	137.5	136.0	134.5	132.9	131.4	132.9	134.5	136.0
105°	176.4	175.8	175.5	175.1	174.3	173.6	172.8	172.0	172.8	173.6	174.3
107.5°	212.2	211.3	210.9	210.7	210.3	210.0	209.6	209.2	209.6	210.0	210.3
110°	249.7	249.0	248.6	248.4	248.0	247.7	247.3	246.9	247.3	247.7	248.0

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	287.3	287.0	286.9	286.5	285.8	285.0	284.3	283.5	284.3	285.0	285.8
115°	322.7	322.8	322.9	322.7	322.3	322.0	321.6	321.2	321.6	322.0	322.3
117.5°	357.8	357.4	357.2	356.9	356.4	355.9	355.4	354.9	355.4	355.9	356.4
120°	391.3	391.4	391.5	391.2	390.7	390.2	389.7	389.2	389.7	390.2	390.7
122.5°	422.7	422.4	422.3	422.2	421.9	421.7	421.4	421.2	421.4	421.7	421.9
125°	453.4	453.7	453.8	453.5	453.0	452.5	452.0	451.5	452.0	452.5	453.0
127.5°	482.2	481.5	481.2	481.1	481.0	480.9	480.7	480.6	480.7	480.9	481.0
130°	509.8	509.4	509.2	509.1	509.0	508.9	508.7	508.6	508.7	508.9	509.0
132.5°	536.3	535.8	535.5	535.4	535.1	534.9	534.6	534.4	534.6	534.9	535.1
135°	560.3	559.8	559.5	559.6	559.7	559.8	560.0	560.1	560.0	559.8	559.7
137.5°	583.9	583.2	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
140°	606.8	606.5	606.4	606.3	606.0	605.7	605.5	605.2	605.5	605.7	606.0
142.5°	627.7	627.6	627.5	627.2	626.7	626.2	625.7	625.2	625.7	626.2	626.7
145°	647.5	647.5	647.5	647.3	646.9	646.6	646.2	645.8	646.2	646.6	646.9
147.5°	665.0	665.1	665.2	664.8	664.1	663.3	662.6	661.8	662.6	663.3	664.1
150°	681.6	681.7	681.8	681.5	681.0	680.5	680.0	679.5	680.0	680.5	681.0
152.5°	695.7	696.0	696.1	695.9	695.5	695.2	694.8	694.4	694.8	695.2	695.5
155°	708.1	708.5	708.7	708.6	708.5	708.4	708.2	708.1	708.2	708.4	708.5
157.5°	719.3	719.8	720.1	720.1	720.1	720.1	720.1	720.1	720.1	720.1	720.1
160°	728.5	728.6	728.7	728.9	729.3	729.6	730.0	730.4	730.0	729.6	729.3
162.5°	737.0	737.1	737.2	737.5	738.0	738.5	739.0	739.5	739.0	738.5	738.0
165°	744.1	744.1	744.1	744.4	745.1	745.7	746.4	747.0	746.4	745.7	745.1
167.5°	750.2	750.3	750.4	750.7	751.4	752.0	752.7	753.3	752.7	752.0	751.4
170°	755.2	755.1	755.0	755.4	756.1	756.9	757.6	758.4	757.6	756.9	756.1
172.5°	758.6	758.5	758.4	758.8	759.5	760.3	761.0	761.8	761.0	760.3	759.5
175°	760.9	760.8	760.7	761.1	761.8	762.6	763.3	764.1	763.3	762.6	761.8
177.5°	762.2	761.9	761.8	762.2	763.1	764.0	764.9	765.8	764.9	764.0	763.1
180°	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	562.4	561.5	560.6	556.9	553.7	548.1	543.5	541.7	541.2	541.7	540.3
5°	546.3	545.8	542.6	536.2	530.2	523.7	519.1	514.5	511.7	511.7	508.5
7.5°	531.1	527.9	525.1	516.8	509.9	501.2	494.2	490.1	487.8	482.7	482.7
10°	515.0	510.4	506.7	498.8	488.7	480.0	471.2	466.1	462.0	458.3	456.9
12.5°	498.8	495.2	488.3	480.0	469.8	458.8	449.6	445.9	436.2	428.4	428.8
15°	483.6	475.4	472.1	460.2	448.2	437.6	424.2	413.6	405.8	400.7	394.3
17.5°	466.6	458.3	452.3	442.2	426.5	409.9	397.1	382.8	374.9	366.2	362.0
20°	447.7	440.8	436.2	420.1	401.2	381.4	367.1	358.4	349.6	343.2	339.5
22.5°	431.6	422.8	417.3	395.7	374.9	355.1	344.1	336.7	329.3	323.8	322.0
25°	410.9	405.8	392.4	373.6	348.2	334.9	325.2	315.5	311.4	307.7	303.5
27.5°	393.8	381.4	372.2	347.3	331.6	316.4	306.8	299.4	294.3	290.6	287.4
30°	372.6	361.1	348.2	327.5	313.2	298.9	290.2	284.2	278.7	276.4	273.6
32.5°	350.5	339.9	327.5	310.9	293.4	282.4	275.4	269.0	265.3	263.0	259.8
35°	330.7	317.4	309.1	293.4	279.1	266.7	260.2	254.7	250.6	249.7	249.2
37.5°	309.5	299.4	291.6	275.4	263.5	252.9	246.9	240.9	238.6	238.1	236.3
40°	291.1	282.4	275.0	259.8	246.9	237.2	232.6	228.9	226.6	226.6	226.2
42.5°	275.0	265.8	258.4	244.6	233.1	224.3	219.3	215.6	214.6	215.1	214.6
45°	257.0	249.2	241.8	227.5	217.9	211.4	205.9	204.1	202.7	203.1	203.6
47.5°	240.0	233.5	226.2	214.6	203.6	196.7	193.5	191.6	191.6	191.6	192.5
50°	224.8	217.4	211.0	199.0	188.9	183.3	180.6	178.3	178.7	179.2	179.6
52.5°	206.8	200.4	195.8	183.8	176.4	169.5	166.3	166.7	166.3	166.3	167.2
55°	191.2	184.7	180.1	169.0	161.7	157.1	154.3	152.9	153.4	152.5	154.3
57.5°	173.7	168.1	164.9	154.3	147.9	143.7	141.4	139.1	140.0	139.6	139.1
60°	158.5	152.0	146.9	139.6	134.0	129.0	127.6	125.3	126.2	125.3	124.8
62.5°	140.9	135.9	132.2	124.8	120.2	116.1	112.9	111.5	111.0	109.6	108.2
65°	123.4	120.7	117.0	109.6	105.0	101.8	100.0	98.6	98.1	94.4	90.3
67.5°	107.3	105.5	101.8	96.3	92.1	88.9	86.1	83.8	81.1	78.3	76.0
70°	92.1	89.4	87.1	82.0	78.3	75.1	72.3	69.6	68.2	65.4	64.5
72.5°	77.4	74.6	72.3	67.7	64.5	61.3	60.3	57.1	55.7	55.3	55.3
75°	62.2	59.9	58.5	54.4	51.6	49.3	47.9	47.0	46.1	45.1	43.8
77.5°	47.4	46.1	45.1	42.4	40.1	38.7	38.2	35.0	34.1	33.2	32.2
80°	34.5	34.1	33.2	30.9	29.9	26.7	26.7	25.8	25.3	25.3	25.3
82.5°	23.5	22.6	22.1	19.8	19.3	18.9	18.4	18.0	18.4	18.0	18.4
85°	12.4	12.0	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.1	11.5
87.5°	4.6	4.6	4.6	4.6	4.1	4.6	4.6	4.1	4.6	4.6	4.6
90°	7.3	8.0	8.5	9.5	10.6	11.6	12.6	13.4	14.1	14.9	15.6
92.5°	7.5	7.4	7.9	8.9	10.0	11.0	12.0	12.8	13.5	14.3	15.0
95°	14.2	12.0	12.1	12.2	12.3	12.5	12.6	13.4	14.1	14.9	15.6
97.5°	71.2	72.6	65.9	52.6	39.3	25.9	12.6	13.2	13.8	14.5	15.1
100°	102.9	104.0	95.2	77.7	60.2	42.6	25.1	22.9	20.8	18.6	16.5
102.5°	137.5	138.3	139.1	140.6	142.1	143.7	145.2	116.6	88.0	59.5	30.9
105°	175.1	175.5	175.8	176.4	177.1	177.7	178.3	179.5	180.6	181.8	182.9
107.5°	210.7	210.9	211.3	212.2	213.1	214.0	214.9	215.5	216.1	216.8	217.4
110°	248.4	248.6	249.0	249.7	250.5	251.2	252.0	252.3	252.5	252.8	253.1

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	286.5	286.9	287.0	287.3	287.5	287.8	288.0	287.9	287.8	287.7	287.6
115°	322.7	322.9	322.8	322.7	322.6	322.4	322.3	322.6	322.8	323.1	323.4
117.5°	356.9	357.2	357.4	357.8	358.1	358.5	358.9	358.8	358.6	358.5	358.4
120°	391.2	391.5	391.4	391.3	391.2	391.0	390.9	391.2	391.4	391.7	392.0
122.5°	422.2	422.3	422.4	422.7	423.0	423.2	423.5	423.6	423.8	423.9	424.0
125°	453.5	453.8	453.7	453.4	453.1	452.9	452.6	453.0	453.4	453.8	454.2
127.5°	481.1	481.2	481.5	482.2	482.8	483.5	484.1	484.0	483.8	483.7	483.6
130°	509.1	509.2	509.4	509.8	510.1	510.5	510.9	511.0	511.2	511.3	511.4
132.5°	535.4	535.5	535.8	536.3	536.8	537.3	537.8	537.9	538.1	538.2	538.3
135°	559.6	559.5	559.8	560.3	560.8	561.3	561.8	562.0	562.3	562.5	562.8
137.5°	582.9	582.9	583.2	583.9	584.5	585.2	585.8	586.0	586.3	586.5	586.8
140°	606.3	606.4	606.5	606.8	607.0	607.3	607.5	607.9	608.3	608.6	609.0
142.5°	627.2	627.5	627.6	627.7	627.8	628.0	628.1	628.3	628.6	628.8	629.1
145°	647.3	647.5	647.5	647.5	647.5	647.5	647.5	647.6	647.8	647.9	648.0
147.5°	664.8	665.2	665.1	665.0	664.9	664.8	664.7	664.8	664.9	665.0	665.1
150°	681.5	681.8	681.7	681.6	681.5	681.3	681.2	681.2	681.2	681.2	681.2
152.5°	695.9	696.1	696.0	695.7	695.5	695.2	695.0	695.2	695.5	695.7	696.0
155°	708.6	708.7	708.5	708.1	707.8	707.4	707.0	707.5	708.0	708.5	709.0
157.5°	720.1	720.1	719.8	719.3	718.8	718.3	717.8	718.4	719.1	719.7	720.4
160°	728.9	728.7	728.6	728.5	728.4	728.2	728.1	728.9	729.6	730.4	731.1
162.5°	737.5	737.2	737.1	737.0	736.9	736.8	736.7	737.5	738.2	739.0	739.7
165°	744.4	744.1	744.1	744.1	744.1	744.1	744.1	745.1	746.1	747.2	748.2
167.5°	750.7	750.4	750.3	750.2	750.1	749.9	749.8	751.0	752.1	753.3	754.4
170°	755.4	755.0	755.1	755.2	755.3	755.4	755.5	756.5	757.5	758.6	759.6
172.5°	758.8	758.4	758.5	758.6	758.7	758.9	759.0	760.0	761.0	762.0	763.0
175°	761.1	760.7	760.8	760.9	761.0	761.2	761.3	762.4	763.6	764.7	765.8
177.5°	762.2	761.8	761.9	762.2	762.5	762.7	763.0	764.0	765.0	766.0	767.0
180°	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	540.3	542.1	539.8	541.2	538.0	537.5	538.0	538.0	538.5	538.9	539.4
5°	509.9	509.4	506.7	504.8	503.5	504.8	505.8	506.7	505.8	506.7	507.1
7.5°	481.3	480.0	478.6	475.4	476.3	475.4	478.1	476.7	476.7	479.0	480.9
10°	456.0	453.2	452.3	448.6	445.9	445.4	448.6	450.0	451.4	452.3	456.0
12.5°	423.3	419.2	415.9	417.3	409.5	412.7	413.6	411.8	417.3	423.8	420.1
15°	388.3	388.8	382.3	380.0	373.6	375.4	375.9	380.5	385.1	384.6	390.1
17.5°	362.5	359.7	354.2	353.8	351.0	352.4	351.9	355.6	354.2	356.5	361.1
20°	338.6	336.7	332.1	330.3	331.2	330.3	330.7	331.2	332.6	337.6	336.7
22.5°	319.7	317.4	317.4	315.1	312.3	311.4	313.7	315.1	316.9	317.8	320.1
25°	303.1	301.2	298.9	297.6	295.3	295.7	297.1	298.9	300.3	302.2	304.0
27.5°	286.0	286.0	283.7	283.3	282.4	281.9	283.7	284.7	284.7	286.0	287.9
30°	272.7	272.7	270.4	269.9	269.5	269.5	270.8	271.3	271.8	273.1	274.1
32.5°	259.8	259.3	258.4	258.9	258.4	258.9	258.9	259.3	260.2	260.7	262.6
35°	247.8	248.3	247.4	247.4	246.9	247.4	248.3	248.7	249.2	250.1	250.1
37.5°	236.3	237.2	236.8	238.1	238.1	238.1	238.1	239.1	239.1	239.1	238.6
40°	226.2	226.2	225.7	226.6	227.5	227.5	228.0	228.0	228.5	228.5	228.0
42.5°	214.6	215.6	217.0	217.4	218.3	217.9	219.3	218.8	219.3	218.3	217.4
45°	204.1	204.1	205.9	207.7	208.2	208.2	208.2	209.1	208.2	206.8	206.4
47.5°	192.5	193.5	194.4	196.7	197.1	197.1	197.1	197.1	196.2	196.2	196.2
50°	181.0	181.5	181.9	182.9	184.2	183.8	183.8	183.8	185.6	183.8	184.2
52.5°	167.2	167.7	168.1	170.0	169.5	169.5	170.0	170.0	171.3	170.9	170.0
55°	153.4	153.4	154.3	154.3	154.3	155.2	155.7	156.6	156.1	156.6	157.1
57.5°	139.6	138.6	138.2	138.2	139.6	139.1	139.6	139.6	141.4	142.3	142.8
60°	123.4	123.4	123.0	120.2	120.2	119.8	121.1	122.1	123.0	127.1	126.7
62.5°	106.9	105.0	103.2	103.6	100.9	102.3	101.3	102.3	105.0	108.2	108.7
65°	90.3	88.9	87.1	86.6	85.7	87.1	86.6	87.1	88.4	90.3	92.6
67.5°	75.5	75.1	74.2	73.7	73.7	73.7	74.6	74.6	75.1	76.5	77.8
70°	64.5	64.0	64.5	63.6	64.0	63.6	64.0	64.5	64.9	65.4	66.8
72.5°	54.4	54.4	54.4	53.4	54.4	53.9	53.9	54.4	54.8	55.3	56.2
75°	43.3	42.4	41.5	40.5	40.1	41.0	41.5	41.0	42.4	44.2	44.2
77.5°	32.7	32.2	32.2	32.2	32.7	32.2	33.2	32.7	33.2	33.2	34.1
80°	25.3	24.9	25.3	25.3	24.9	25.8	25.3	25.3	25.8	26.3	25.8
82.5°	18.4	18.9	18.4	18.4	18.4	19.3	18.4	18.4	18.4	18.9	18.9
85°	11.5	11.5	11.5	11.5	12.0	11.5	12.0	11.5	12.4	12.0	12.0
87.5°	4.1	4.6	5.1	5.1	5.1	5.1	4.6	5.1	5.5	5.1	5.5
90°	16.0	16.1	16.4	16.6	16.9	17.1	16.9	16.6	16.4	16.1	16.0
92.5°	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4
95°	16.0	16.1	16.2	16.3	16.5	16.6	16.5	16.3	16.2	16.1	16.0
97.5°	15.4	15.5	15.6	15.7	15.9	16.0	15.9	15.7	15.6	15.5	15.4
100°	15.4	15.5	15.6	15.7	15.9	16.0	15.9	15.7	15.6	15.5	15.4
102.5°	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6
105°	183.5	181.2	176.6	172.1	167.5	162.9	167.5	172.1	176.6	181.2	183.5
107.5°	217.7	218.0	218.5	219.0	219.5	220.0	219.5	219.0	218.5	218.0	217.7
110°	253.2	253.4	253.8	254.1	254.5	254.9	254.5	254.1	253.8	253.4	253.2

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	287.5	287.8	288.3	288.8	289.3	289.8	289.3	288.8	288.3	287.8	287.5
115°	323.5	323.5	323.5	323.5	323.5	323.5	323.5	323.5	323.5	323.5	323.5
117.5°	358.3	358.3	358.3	358.3	358.3	358.3	358.3	358.3	358.3	358.3	358.3
120°	392.1	392.0	391.7	391.4	391.2	390.9	391.2	391.4	391.7	392.0	392.1
122.5°	424.1	424.0	423.7	423.4	423.2	422.9	423.2	423.4	423.7	424.0	424.1
125°	454.4	454.5	454.6	454.7	454.8	454.9	454.8	454.7	454.6	454.5	454.4
127.5°	483.5	483.4	483.3	483.2	483.0	482.9	483.0	483.2	483.3	483.4	483.5
130°	511.5	511.5	511.5	511.5	511.5	511.5	511.5	511.5	511.5	511.5	511.5
132.5°	538.4	538.3	538.2	538.1	537.9	537.8	537.9	538.1	538.2	538.3	538.4
135°	562.9	563.0	563.3	563.6	563.8	564.1	563.8	563.6	563.3	563.0	562.9
137.5°	586.9	586.8	586.7	586.6	586.5	586.4	586.5	586.6	586.7	586.8	586.9
140°	609.2	609.3	609.4	609.5	609.7	609.8	609.7	609.5	609.4	609.3	609.2
142.5°	629.2	629.2	629.2	629.2	629.2	629.2	629.2	629.2	629.2	629.2	629.2
145°	648.1	648.2	648.5	648.7	649.0	649.2	649.0	648.7	648.5	648.2	648.1
147.5°	665.2	665.3	665.4	665.5	665.7	665.8	665.7	665.5	665.4	665.3	665.2
150°	681.2	681.3	681.4	681.5	681.7	681.8	681.7	681.5	681.4	681.3	681.2
152.5°	696.1	696.0	695.9	695.8	695.6	695.5	695.6	695.8	695.9	696.0	696.1
155°	709.2	709.0	708.6	708.3	707.9	707.5	707.9	708.3	708.6	709.0	709.2
157.5°	720.7	720.4	719.7	719.1	718.4	717.8	718.4	719.1	719.7	720.4	720.7
160°	731.5	731.1	730.4	729.6	728.9	728.1	728.9	729.6	730.4	731.1	731.5
162.5°	740.1	739.7	738.8	737.9	737.0	736.1	737.0	737.9	738.8	739.7	740.1
165°	748.7	748.1	747.0	745.8	744.7	743.5	744.7	745.8	747.0	748.1	748.7
167.5°	755.0	754.4	753.1	751.8	750.5	749.2	750.5	751.8	753.1	754.4	755.0
170°	760.1	759.5	758.2	756.9	755.7	754.4	755.7	756.9	758.2	759.5	760.1
172.5°	763.5	762.8	761.4	760.1	758.7	757.3	758.7	760.1	761.4	762.8	763.5
175°	766.4	765.6	764.1	762.6	761.0	759.5	761.0	762.6	764.1	765.6	766.4
177.5°	767.5	766.7	765.2	763.7	762.2	760.7	762.2	763.7	765.2	766.7	767.5
180°	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	541.2	543.5	542.6	539.4	540.8	543.5	546.3	550.0	552.3	554.1	555.0
5°	509.4	513.6	512.7	512.7	514.5	519.1	523.7	531.6	534.3	537.5	542.1
7.5°	481.3	484.6	487.3	488.3	491.0	497.0	503.0	511.7	518.7	522.3	525.1
10°	456.5	458.8	462.9	465.2	468.0	475.4	484.1	493.3	500.2	506.7	510.4
12.5°	424.7	433.9	439.4	443.1	446.8	457.9	464.8	474.9	483.2	489.2	494.7
15°	389.2	400.3	403.5	417.8	427.0	435.7	446.3	458.3	466.1	473.1	480.4
17.5°	359.3	367.1	370.8	386.0	393.8	407.6	422.8	438.0	450.0	455.1	462.5
20°	340.4	344.5	351.9	357.0	365.3	381.4	398.0	416.4	434.4	439.4	446.8
22.5°	321.0	326.6	331.6	338.6	345.0	356.1	372.6	392.9	412.3	421.5	430.2
25°	303.5	309.1	312.3	319.7	325.7	336.7	348.2	369.0	392.0	399.8	413.6
27.5°	289.7	293.0	298.5	301.7	308.6	318.7	329.3	345.0	367.6	380.9	394.3
30°	275.9	278.2	282.8	287.4	292.5	299.4	311.4	326.6	347.3	358.8	372.2
32.5°	262.1	265.8	268.5	271.8	277.3	285.6	293.9	308.6	325.2	338.1	351.5
35°	250.6	252.0	255.6	259.3	263.0	270.4	279.1	293.4	308.2	318.3	330.3
37.5°	238.1	240.4	243.2	244.6	250.6	255.2	264.4	275.4	293.0	299.4	311.4
40°	228.5	228.0	230.8	233.1	235.8	243.2	248.7	260.7	274.5	284.7	292.0
42.5°	216.5	216.5	217.4	220.2	223.9	228.5	234.9	245.0	259.3	266.7	275.4
45°	206.8	205.4	205.9	207.7	210.0	214.6	221.1	229.8	244.1	250.1	259.3
47.5°	195.3	193.9	193.9	195.8	197.6	200.8	205.9	216.0	227.5	235.4	242.3
50°	182.4	182.9	182.4	183.8	184.7	187.9	193.5	201.7	212.3	218.8	226.6
52.5°	170.4	169.5	169.0	170.0	171.8	174.1	180.1	187.5	197.6	204.1	211.0
55°	155.7	156.6	156.6	156.6	159.4	160.3	164.9	172.3	182.4	187.5	193.9
57.5°	142.3	141.9	142.8	142.3	144.6	147.9	151.5	157.1	167.2	172.3	178.3
60°	127.6	128.1	128.5	128.5	130.4	133.6	137.7	142.8	151.1	156.1	161.7
62.5°	109.6	111.9	114.2	115.2	117.9	120.2	123.0	128.5	135.9	139.6	144.6
65°	92.6	95.8	99.0	101.3	103.2	105.5	109.2	114.2	120.2	123.9	129.0
67.5°	77.8	80.1	84.3	86.6	90.3	93.0	95.3	99.5	106.9	108.2	112.4
70°	67.2	68.2	70.0	71.9	76.0	78.3	81.1	85.2	90.7	94.0	96.3
72.5°	56.7	57.1	58.0	59.9	61.7	64.5	67.7	71.4	76.5	77.8	81.1
75°	45.1	47.9	47.9	49.3	50.7	52.0	54.8	58.5	61.7	64.0	65.9
77.5°	33.6	35.0	35.9	38.2	40.1	41.5	43.3	46.1	47.9	49.7	51.1
80°	26.3	26.7	27.2	27.2	28.1	29.9	31.8	33.6	35.9	36.8	38.2
82.5°	19.3	19.3	19.3	20.3	20.7	21.2	21.2	22.1	24.4	25.3	26.7
85°	12.4	12.4	12.4	12.4	12.9	13.4	13.8	14.3	14.3	14.3	15.2
87.5°	5.1	6.0	5.5	6.0	6.0	6.0	6.0	6.4	6.4	6.9	6.9
90°	15.6	14.9	14.1	13.4	12.6	11.6	10.6	9.5	8.5	8.0	7.3
92.5°	15.0	14.3	13.5	12.8	12.0	11.0	10.0	8.9	7.9	7.4	7.5
95°	15.6	14.9	14.1	13.4	12.6	12.5	12.3	12.2	12.1	12.0	14.2
97.5°	15.1	14.5	13.8	13.2	12.6	25.9	39.3	52.6	65.9	72.6	71.2
100°	16.5	18.6	20.8	22.9	25.1	42.6	60.2	77.7	95.2	104.0	102.9
102.5°	30.9	59.5	88.0	116.6	145.2	143.7	142.1	140.6	139.1	138.3	137.5
105°	182.9	181.8	180.6	179.5	178.3	177.7	177.1	176.4	175.8	175.5	175.1
107.5°	217.4	216.8	216.1	215.5	214.9	214.0	213.1	212.2	211.3	210.9	210.7
110°	253.1	252.8	252.5	252.3	252.0	251.2	250.5	249.7	249.0	248.6	248.4

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	287.6	287.7	287.8	287.9	288.0	287.8	287.5	287.3	287.0	286.9	286.5
115°	323.4	323.1	322.8	322.6	322.3	322.4	322.6	322.7	322.8	322.9	322.7
117.5°	358.4	358.5	358.6	358.8	358.9	358.5	358.1	357.8	357.4	357.2	356.9
120°	392.0	391.7	391.4	391.2	390.9	391.0	391.2	391.3	391.4	391.5	391.2
122.5°	424.0	423.9	423.8	423.6	423.5	423.2	423.0	422.7	422.4	422.3	422.2
125°	454.2	453.8	453.4	453.0	452.6	452.9	453.1	453.4	453.7	453.8	453.5
127.5°	483.6	483.7	483.8	484.0	484.1	483.5	482.8	482.2	481.5	481.2	481.1
130°	511.4	511.3	511.2	511.0	510.9	510.5	510.1	509.8	509.4	509.2	509.1
132.5°	538.3	538.2	538.1	537.9	537.8	537.3	536.8	536.3	535.8	535.5	535.4
135°	562.8	562.5	562.3	562.0	561.8	561.3	560.8	560.3	559.8	559.5	559.6
137.5°	586.8	586.5	586.3	586.0	585.8	585.2	584.5	583.9	583.2	582.9	582.9
140°	609.0	608.6	608.3	607.9	607.5	607.3	607.0	606.8	606.5	606.4	606.3
142.5°	629.1	628.8	628.6	628.3	628.1	628.0	627.8	627.7	627.6	627.5	627.2
145°	648.0	647.9	647.8	647.6	647.5	647.5	647.5	647.5	647.5	647.5	647.3
147.5°	665.1	665.0	664.9	664.8	664.7	664.8	664.9	665.0	665.1	665.2	664.8
150°	681.2	681.2	681.2	681.2	681.2	681.3	681.5	681.6	681.7	681.8	681.5
152.5°	696.0	695.7	695.5	695.2	695.0	695.2	695.5	695.7	696.0	696.1	695.9
155°	709.0	708.5	708.0	707.5	707.0	707.4	707.8	708.1	708.5	708.7	708.6
157.5°	720.4	719.7	719.1	718.4	717.8	718.3	718.8	719.3	719.8	720.1	720.1
160°	731.1	730.4	729.6	728.9	728.1	728.2	728.4	728.5	728.6	728.7	728.9
162.5°	739.7	739.0	738.2	737.5	736.7	736.8	736.9	737.0	737.1	737.2	737.5
165°	748.2	747.2	746.1	745.1	744.1	744.1	744.1	744.1	744.1	744.1	744.4
167.5°	754.4	753.3	752.1	751.0	749.8	749.9	750.1	750.2	750.3	750.4	750.7
170°	759.6	758.6	757.5	756.5	755.5	755.4	755.3	755.2	755.1	755.0	755.4
172.5°	763.0	762.0	761.0	760.0	759.0	758.9	758.7	758.6	758.5	758.4	758.8
175°	765.8	764.7	763.6	762.4	761.3	761.2	761.0	760.9	760.8	760.7	761.1
177.5°	767.0	766.0	765.0	764.0	763.0	762.7	762.5	762.2	761.9	761.8	762.2
180°	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1	764.1

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	571.6	571.6	571.6	571.6
2.5°	558.7	561.5	566.1	572.5
5°	545.8	553.7	561.0	570.7
7.5°	534.3	543.5	553.7	567.5
10°	521.0	532.5	545.4	562.4
12.5°	505.3	521.4	536.2	554.6
15°	493.8	505.8	524.6	546.3
17.5°	477.7	493.8	512.7	537.1
20°	462.5	479.5	500.7	526.0
22.5°	446.3	465.7	486.9	514.0
25°	429.8	450.5	471.7	500.7
27.5°	414.6	433.4	457.4	486.9
30°	396.1	417.8	440.8	471.7
32.5°	378.2	400.7	424.2	455.1
35°	358.8	381.4	407.2	436.7
37.5°	339.9	364.8	388.3	416.9
40°	319.2	345.0	369.4	398.4
42.5°	298.9	325.7	350.1	374.9
45°	280.1	306.3	328.4	351.9
47.5°	262.1	285.6	308.2	329.3
50°	244.6	264.4	285.1	302.6
52.5°	226.2	245.0	261.6	277.3
55°	209.6	224.3	239.1	253.3
57.5°	189.8	204.5	217.4	228.5
60°	173.2	182.4	194.8	206.4
62.5°	154.3	164.9	174.6	181.9
65°	135.9	145.1	152.5	158.9
67.5°	120.2	125.7	131.3	138.2
70°	101.3	105.9	112.4	117.5
72.5°	85.2	88.9	92.1	98.1
75°	69.1	72.3	74.2	79.7
77.5°	53.4	56.7	58.0	61.3
80°	41.0	41.5	43.3	46.1
82.5°	28.1	29.0	29.5	31.8
85°	16.1	18.4	18.0	18.9
87.5°	6.9	7.4	8.3	9.2
90°	5.9	4.5	3.1	1.7
92.5°	7.8	8.1	8.3	8.6
95°	18.5	22.8	27.1	31.4
97.5°	68.4	65.6	62.8	60.0
100°	100.6	98.3	96.0	93.7
102.5°	136.0	134.5	132.9	131.4
105°	174.3	173.6	172.8	172.0
107.5°	210.3	210.0	209.6	209.2
110°	248.0	247.7	247.3	246.9

TEST NUMBER: P1026325

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	285.8	285.0	284.3	283.5
115°	322.3	322.0	321.6	321.2
117.5°	356.4	355.9	355.4	354.9
120°	390.7	390.2	389.7	389.2
122.5°	421.9	421.7	421.4	421.2
125°	453.0	452.5	452.0	451.5
127.5°	481.0	480.9	480.7	480.6
130°	509.0	508.9	508.7	508.6
132.5°	535.1	534.9	534.6	534.4
135°	559.7	559.8	560.0	560.1
137.5°	582.9	582.9	582.9	582.9
140°	606.0	605.7	605.5	605.2
142.5°	626.7	626.2	625.7	625.2
145°	646.9	646.6	646.2	645.8
147.5°	664.1	663.3	662.6	661.8
150°	681.0	680.5	680.0	679.5
152.5°	695.5	695.2	694.8	694.4
155°	708.5	708.4	708.2	708.1
157.5°	720.1	720.1	720.1	720.1
160°	729.3	729.6	730.0	730.4
162.5°	738.0	738.5	739.0	739.5
165°	745.1	745.7	746.4	747.0
167.5°	751.4	752.0	752.7	753.3
170°	756.1	756.9	757.6	758.4
172.5°	759.5	760.3	761.0	761.8
175°	761.8	762.6	763.3	764.1
177.5°	763.1	764.0	764.9	765.8
180°	764.1	764.1	764.1	764.1

(END OF REPORT)