

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026327

Luminaire Tested: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026327
REPORT IS A COMBINATION OF REPORTS P999357 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D590UB30-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3565.0 lumens
Efficiency: N/A
Efficacy: 125.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	38	36	35
3	80	71	64	59	73	65	59	54	54	50	46	44	40	38	34	32	30
4	74	63	56	50	67	58	51	46	48	43	39	39	36	33	30	28	26
5	68	56	49	43	61	52	45	40	43	38	34	35	31	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18
8	53	41	34	29	49	38	32	27	32	27	23	26	23	20	21	18	16
9	50	38	31	26	45	35	29	24	30	24	21	24	21	18	20	17	15
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4661	4661	4661	4661
5°	4661	5267	4669	4025
10°	4636	6072	4633	3501
15°	4581	6834	4581	2931
20°	4523	7409	4500	2582
25°	4453	7440	4433	2331
30°	4378	6327	4344	2160
35°	4272	4774	4218	2032
40°	4154	3459	4072	1931
45°	3959	2629	3861	1843
50°	3728	2125	3626	1713
55°	3477	1759	3363	1540
60°	3226	1488	3081	1281
65°	2910	1212	2817	1019
70°	2621	982	2496	827
75°	2297	708	2138	606
80°	1896	470	1723	446
85°	1375	241	1142	241

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 5835 cd/sqm

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.4	1.6
10°-20°	167.2	4.7
20°-30°	261.8	7.3
30°-40°	290.8	8.2
40°-50°	257.6	7.2
50°-60°	200.8	5.6
60°-70°	131.3	3.7
70°-80°	64.4	1.8
80°-90°	16.8	0.5
90°-100°	210.8	5.9
100°-110°	440.2	12.3
110°-120°	391.3	11.0
120°-130°	329.4	9.2
130°-140°	274.8	7.7
140°-150°	209.8	5.9
150°-160°	147.5	4.1
160°-170°	86.8	2.4
170°-180°	28.2	0.8
0°-30°	484.3	13.6
0°-40°	775.1	21.7
0°-60°	1233.5	34.6
0°-90°	1446.1	40.6
90°-120°	1042.3	29.2
90°-150°	1856.4	52.1
90°-180°	2119.0	59.4
0°-180°	3565.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	572	572	572	572	572	
5°	571	660	572	505	571	54
15°	546	875	546	375	546	154
25°	501	944	498	296	501	231
35°	437	581	431	247	437	273
45°	352	297	343	208	352	271
55°	253	177	245	155	253	227
65°	159	104	154	87	159	158
75°	80	48	74	41	80	85
85°	19	12	16	12	19	21
90°	1	12	1	12	1	3
95°	19	140	19	140	19	21
105°	67	804	67	804	67	71
115°	118	772	118	772	118	117
125°	164	616	164	616	164	146
135°	195	551	195	551	195	151
145°	225	450	225	450	225	141
155°	256	377	256	377	256	118
165°	278	329	278	329	278	79
175°	290	296	290	296	290	28
180°	291	291	291	291	291	

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	572.5	577.6	580.4	582.7	587.3	589.1	592.8	593.7	597.4	597.0	595.6
5°	570.7	579.5	585.9	592.8	601.1	605.7	610.8	618.1	621.8	626.9	630.1
7.5°	567.5	579.5	590.0	600.6	614.0	621.4	627.8	639.3	649.0	657.3	666.5
10°	562.4	577.6	593.3	607.6	626.0	634.7	644.4	661.4	674.8	686.3	701.1
12.5°	554.6	575.8	593.3	612.6	636.1	648.1	661.0	681.3	696.9	715.8	734.2
15°	546.3	569.8	592.8	618.1	644.9	658.7	671.6	698.8	722.7	744.4	764.6
17.5°	537.1	562.9	588.2	616.3	648.5	665.6	680.8	713.5	739.7	767.8	788.1
20°	526.0	554.1	583.1	614.5	650.9	669.7	686.8	724.1	753.1	783.5	808.8
22.5°	514.0	544.4	576.2	610.3	648.1	668.8	688.6	728.7	762.3	790.4	824.5
25°	500.7	532.9	565.6	601.6	643.9	666.5	686.8	726.4	762.3	799.2	832.3
27.5°	486.9	520.0	554.1	591.9	635.2	657.3	680.3	718.6	760.5	800.6	834.2
30°	471.7	503.9	539.8	575.8	621.8	643.9	667.4	708.9	754.5	794.6	831.0
32.5°	455.1	488.3	522.3	559.6	604.8	628.7	650.4	697.4	743.9	783.5	817.6
35°	436.7	468.0	500.2	538.5	583.1	604.8	630.6	679.4	726.4	768.3	790.4
37.5°	416.9	446.8	476.7	514.5	557.3	583.6	608.9	658.2	708.0	736.1	747.6
40°	398.4	424.7	450.9	487.3	530.6	557.8	583.6	634.7	678.5	700.1	691.4
42.5°	374.9	402.1	425.6	459.2	503.0	528.3	554.6	607.6	643.0	651.8	630.1
45°	351.9	374.5	397.1	429.8	475.8	497.5	525.6	574.8	604.3	596.5	564.7
47.5°	329.3	347.8	369.0	400.7	442.2	468.0	494.2	537.1	557.8	546.8	502.5
50°	302.6	321.0	343.2	370.8	410.9	435.7	456.5	496.1	511.7	484.6	431.1
52.5°	277.3	293.4	312.3	338.1	376.3	398.9	421.5	455.5	460.6	429.3	373.1
55°	253.3	266.2	286.0	306.8	341.8	365.7	381.4	410.4	409.0	369.9	321.5
57.5°	228.5	240.4	253.8	275.4	308.6	326.6	343.6	369.0	355.6	322.4	274.5
60°	206.4	213.3	226.6	247.4	275.4	291.1	304.5	318.3	306.8	270.8	234.0
62.5°	181.9	189.8	199.4	216.0	240.9	255.6	265.3	271.3	259.3	231.7	198.1
65°	158.9	165.8	176.0	190.7	209.6	220.6	225.7	229.8	223.4	192.1	165.4
67.5°	138.2	142.8	152.0	161.7	181.9	184.7	191.6	193.5	180.6	156.6	135.4
70°	117.5	122.1	126.2	137.7	146.9	152.0	153.4	153.4	140.5	124.8	107.3
72.5°	98.1	100.9	105.0	112.9	117.9	121.6	123.4	121.1	109.2	96.3	83.4
75°	79.7	81.1	84.8	89.8	94.0	92.6	92.1	89.4	80.6	71.4	64.0
77.5°	61.3	62.2	66.3	67.7	67.7	69.1	67.2	64.5	57.1	50.2	47.0
80°	46.1	47.4	47.9	48.8	47.9	47.9	46.5	41.9	38.2	35.0	32.7
82.5°	31.8	32.7	33.2	31.8	32.7	31.3	29.0	25.8	23.5	23.0	22.1
85°	18.9	19.3	18.9	18.9	17.5	17.0	15.2	14.7	13.8	13.8	13.4
87.5°	9.2	8.8	7.8	6.9	6.9	6.4	6.9	6.0	6.9	6.4	6.0
90°	0.6	1.7	3.4	4.0	4.6	4.6	4.6	8.0	8.0	9.1	10.3
92.5°	8.0	11.4	17.7	26.3	36.6	44.0	51.4	86.9	142.3	196.0	224.0
95°	18.9	20.6	26.3	33.7	47.4	59.4	71.4	121.2	214.9	351.5	465.8
97.5°	31.4	31.4	36.6	43.4	55.4	65.7	76.0	115.5	196.0	336.6	498.4
100°	43.4	43.4	47.4	54.3	65.2	74.3	83.4	117.2	181.8	298.4	459.5
102.5°	54.9	56.0	59.4	65.7	76.0	84.6	93.2	122.9	177.8	272.6	410.9
105°	66.9	68.6	71.4	78.3	88.6	96.9	105.2	132.6	180.0	260.1	374.9
107.5°	80.0	81.2	84.0	91.4	101.2	109.4	117.7	142.9	186.9	256.6	351.5
110°	93.2	94.3	97.2	104.0	114.3	122.0	129.7	154.9	194.9	257.8	340.6

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	105.7	106.9	110.3	116.6	126.9	134.6	142.3	166.3	203.5	261.2	335.5
115°	117.7	119.5	123.5	129.2	140.0	147.8	155.5	178.3	212.6	265.8	334.4
117.5°	130.3	132.0	135.5	141.7	152.0	160.0	168.0	189.8	221.8	270.3	333.8
120°	142.9	144.0	148.0	154.3	164.0	172.0	180.0	201.8	231.5	275.5	333.8
122.5°	154.3	155.5	159.5	165.2	176.0	183.8	191.5	213.2	240.6	280.6	333.2
125°	164.0	166.3	169.8	176.0	186.9	194.9	202.9	223.5	249.8	285.8	332.6
127.5°	173.2	174.9	178.9	185.8	197.2	205.2	213.2	233.2	257.8	289.8	331.5
130°	180.6	182.9	187.5	196.0	206.9	215.2	223.5	242.9	265.2	294.4	330.9
132.5°	188.0	189.8	196.0	204.0	216.0	223.8	231.5	250.9	272.6	298.4	330.4
135°	194.9	197.2	202.9	212.6	224.6	232.0	239.5	258.3	278.9	302.4	329.8
137.5°	201.8	204.0	210.3	219.5	232.1	239.2	246.3	264.1	283.5	304.6	329.8
140°	209.2	210.9	217.2	226.9	238.9	245.8	252.6	269.8	288.1	307.5	329.2
142.5°	217.2	218.9	224.6	233.8	245.2	251.8	258.3	274.9	291.5	309.8	329.2
145°	224.6	226.3	232.1	240.1	250.9	257.2	263.5	278.3	293.8	310.4	328.1
147.5°	233.2	233.8	238.9	247.5	256.6	262.4	268.1	282.3	296.1	310.9	326.4
150°	241.2	241.8	246.3	253.2	261.8	267.2	272.6	285.2	297.8	310.9	324.6
152.5°	248.6	248.6	253.2	259.5	266.9	271.8	276.6	287.5	298.9	309.8	321.8
155°	255.5	256.1	259.5	265.2	271.5	275.8	280.1	289.8	299.5	308.6	318.9
157.5°	262.3	262.3	265.8	270.3	276.1	279.5	282.9	291.5	299.5	307.5	316.1
160°	268.6	268.6	270.9	274.9	279.5	282.6	285.8	292.6	299.5	305.8	312.6
162.5°	274.3	273.8	275.5	278.9	282.9	285.2	287.5	293.8	299.5	304.1	309.2
165°	278.3	278.3	279.5	282.3	285.2	286.9	288.6	293.8	298.4	301.8	305.8
167.5°	282.9	282.3	282.9	285.2	286.9	288.4	289.8	293.8	297.2	299.5	302.4
170°	285.8	285.2	285.8	287.5	288.6	289.5	290.4	293.2	296.1	297.2	298.9
172.5°	288.6	288.1	288.1	289.2	289.8	290.4	290.9	292.6	294.9	294.9	295.5
175°	290.4	289.8	289.8	290.4	290.9	290.9	290.9	292.1	293.8	293.2	293.2
177.5°	291.5	290.9	290.4	290.9	290.9	290.9	290.9	291.5	292.6	291.5	291.5
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	599.3	604.3	604.8	609.4	608.0	605.7	609.9	607.1	612.6	610.8	613.1
5°	634.3	641.2	647.2	650.9	657.3	655.9	662.8	660.5	665.6	660.5	667.0
7.5°	675.3	686.8	692.8	702.4	705.2	705.7	714.0	715.8	719.0	715.8	719.5
10°	715.3	729.2	743.0	750.8	755.9	762.8	770.2	773.4	775.7	772.5	774.8
12.5°	751.7	773.4	788.6	804.2	807.9	813.9	821.7	820.8	830.0	828.2	832.3
15°	785.4	809.3	827.7	840.2	850.3	855.4	870.1	871.0	870.6	875.2	872.4
17.5°	815.3	835.6	861.8	877.9	890.4	890.4	898.7	915.7	914.3	913.9	916.6
20°	839.7	862.7	887.1	914.3	924.5	926.3	937.8	946.6	947.9	947.9	947.9
22.5°	858.1	885.3	911.6	930.9	938.7	945.2	955.3	960.8	962.7	961.8	962.7
25°	867.3	893.1	919.9	937.4	942.0	945.6	946.6	949.8	949.3	943.8	947.0
27.5°	869.2	894.1	911.6	916.2	913.9	911.6	896.8	898.2	894.1	885.8	889.0
30°	860.9	874.2	873.8	859.5	855.4	845.7	832.3	812.5	796.4	789.5	791.8
32.5°	831.0	831.0	814.4	782.1	767.8	750.3	726.4	708.4	687.2	682.6	691.4
35°	789.5	766.0	735.6	693.2	671.6	658.7	617.2	604.3	586.4	581.3	585.4
37.5°	725.0	685.9	641.6	602.0	583.6	560.6	524.2	505.8	492.9	484.1	488.3
40°	652.7	605.2	559.2	510.4	490.1	471.2	444.0	427.5	406.7	407.6	409.0
42.5°	583.6	527.9	476.3	431.1	411.8	396.1	377.2	357.0	349.6	347.3	345.0
45°	510.4	450.9	402.6	369.0	351.5	336.7	319.2	307.7	298.9	297.1	299.4
47.5°	441.3	391.1	345.0	313.7	299.4	292.0	278.2	267.6	262.1	257.5	260.2
50°	378.6	331.6	294.8	268.5	258.4	253.3	240.4	234.9	229.4	228.0	227.5
52.5°	327.0	287.0	255.2	234.0	226.2	223.4	213.7	205.9	201.3	202.7	203.6
55°	280.1	246.0	221.1	204.1	197.6	194.4	187.5	181.9	178.7	177.3	178.3
57.5°	238.6	209.1	191.2	177.3	172.3	170.9	163.5	161.7	159.4	158.0	158.0
60°	200.8	180.1	163.5	155.7	150.2	148.8	143.3	140.9	140.5	139.1	138.2
62.5°	169.0	152.0	140.5	132.2	129.9	129.4	125.7	123.0	121.6	120.7	120.7
65°	141.4	129.0	119.3	113.3	111.5	110.5	106.4	105.5	104.6	103.6	103.2
67.5°	117.9	106.9	100.0	95.8	93.5	94.0	91.7	89.8	89.8	89.4	88.9
70°	95.3	88.4	82.5	80.1	79.2	78.3	77.4	76.0	75.5	75.5	75.5
72.5°	75.1	70.5	67.2	65.9	64.9	64.0	63.1	63.1	63.1	62.6	62.6
75°	57.6	55.7	53.4	52.0	52.0	53.0	51.6	50.2	48.8	47.9	48.4
77.5°	43.3	42.4	41.0	38.7	39.2	38.2	38.2	37.3	37.8	37.8	36.8
80°	31.8	30.4	29.9	28.6	29.0	28.6	28.1	28.1	27.2	27.2	27.2
82.5°	22.1	20.7	20.7	20.3	19.8	19.8	19.3	19.3	19.8	18.9	18.9
85°	13.4	12.9	12.9	12.0	12.0	12.0	12.0	12.4	12.0	11.5	11.5
87.5°	6.0	6.4	6.0	5.5	5.5	5.5	5.1	5.1	4.6	5.1	5.1
90°	9.7	10.3	10.9	11.4	11.4	11.4	12.0	12.6	12.0	12.0	12.0
92.5°	186.3	137.7	102.9	81.2	74.1	66.9	58.3	54.3	52.0	52.0	52.0
95°	479.0	423.5	334.9	258.3	230.6	202.9	174.9	157.2	146.9	139.5	146.9
97.5°	600.7	609.8	565.8	503.0	471.0	439.0	400.1	365.8	348.6	334.9	348.6
100°	605.8	689.3	700.7	672.7	651.6	630.4	580.7	545.8	528.7	524.1	528.7
102.5°	563.0	685.3	753.3	770.5	764.8	759.0	733.3	710.4	692.2	688.7	692.2
105°	509.3	640.1	739.0	795.6	807.3	819.0	820.2	815.6	807.6	804.2	807.6
107.5°	465.2	584.7	691.6	770.5	794.5	818.5	843.6	853.9	858.5	859.0	858.5
110°	433.8	535.5	634.4	717.3	748.8	780.2	820.8	844.8	855.0	860.2	855.0

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	416.1	499.5	584.1	661.3	692.8	724.2	771.6	801.9	817.3	826.5	817.3
115°	406.4	477.8	548.1	615.0	642.4	669.9	715.0	749.3	767.6	772.2	767.6
117.5°	401.2	465.2	524.7	579.0	603.0	627.0	667.0	696.7	716.2	719.0	716.2
120°	397.2	457.2	510.4	556.1	576.4	596.7	629.3	654.4	669.3	675.6	669.3
122.5°	392.7	450.4	501.3	541.8	559.0	576.1	602.4	623.0	635.0	641.3	635.0
125°	387.5	442.4	491.5	531.0	546.7	562.4	585.3	601.8	612.7	616.1	612.7
127.5°	380.7	433.2	480.7	520.1	535.0	549.8	572.7	587.6	596.7	600.1	596.7
130°	374.4	421.8	467.0	505.8	521.0	536.1	559.6	573.8	583.0	586.4	583.0
132.5°	368.7	409.8	451.5	489.3	504.4	519.5	542.4	559.0	567.6	571.0	567.6
135°	362.9	398.9	436.1	471.0	485.2	499.5	522.4	538.4	547.5	551.0	547.5
137.5°	357.8	388.7	421.2	451.5	464.6	477.8	499.5	516.1	523.5	527.5	523.5
140°	353.8	380.1	406.9	432.7	444.7	456.7	476.7	489.3	497.3	501.8	497.3
142.5°	350.4	372.1	394.9	416.1	426.1	436.1	453.2	464.7	471.5	474.4	471.5
145°	346.4	364.7	384.1	401.2	409.2	417.2	431.5	441.2	447.0	449.8	447.0
147.5°	342.9	358.4	374.4	388.7	395.2	401.8	412.7	421.2	425.8	427.0	425.8
150°	338.9	352.6	365.8	377.2	382.4	387.5	396.7	404.1	407.5	408.1	407.5
152.5°	334.4	346.4	357.2	367.5	371.5	375.5	382.9	388.7	390.4	390.9	390.4
155°	329.8	340.1	349.2	357.8	361.2	364.7	370.4	374.9	376.7	376.7	376.7
157.5°	325.2	333.2	341.2	348.6	351.5	354.4	358.9	362.4	363.5	363.5	363.5
160°	320.1	326.9	333.2	339.5	341.8	344.1	347.5	350.9	351.5	351.5	351.5
162.5°	315.5	320.6	325.8	330.4	332.4	334.4	336.6	340.1	340.6	340.1	340.6
165°	310.4	314.9	318.4	322.4	323.8	325.2	327.5	329.8	329.2	328.6	329.2
167.5°	305.8	309.2	312.1	315.5	316.4	317.2	318.4	320.1	320.1	319.5	320.1
170°	301.2	304.1	305.8	308.1	309.0	309.8	310.9	311.5	310.9	310.9	310.9
172.5°	297.2	299.5	300.6	301.8	302.4	302.9	303.5	304.1	303.5	302.4	303.5
175°	294.4	295.5	296.1	297.2	297.2	297.2	297.2	298.4	297.2	296.1	297.2
177.5°	292.1	292.6	293.2	293.2	293.5	293.8	293.2	293.8	292.6	291.5	292.6
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	614.5	611.2	610.8	610.8	605.7	608.5	602.9	597.0	594.2	594.2	589.1
5°	665.6	662.4	659.1	654.1	654.1	651.3	642.6	633.8	627.4	621.8	615.8
7.5°	718.1	714.9	705.7	700.6	703.4	697.8	686.3	671.6	660.5	651.8	639.3
10°	775.2	766.5	761.9	759.1	749.4	743.4	730.1	708.4	694.6	683.1	667.0
12.5°	821.7	824.5	807.0	808.4	798.7	790.4	769.7	749.0	728.2	712.1	688.2
15°	871.9	863.7	853.1	844.8	841.5	831.4	813.9	786.3	763.7	738.4	711.2
17.5°	911.6	905.1	895.0	887.1	880.2	855.8	841.1	816.7	785.8	760.9	727.8
20°	945.2	939.2	924.9	919.9	907.4	889.9	868.7	831.0	803.3	776.1	743.9
22.5°	959.5	953.5	941.0	934.6	926.8	909.7	889.4	853.5	819.4	785.4	751.3
25°	947.5	947.5	941.5	939.2	932.3	917.1	896.4	866.0	829.6	792.7	752.2
27.5°	889.4	901.0	905.1	907.4	907.4	907.9	893.6	864.1	828.6	792.7	750.3
30°	805.6	825.0	842.0	847.1	855.8	865.5	871.5	857.2	825.4	787.7	745.3
32.5°	700.1	725.0	756.8	764.6	776.6	805.6	821.7	827.7	810.2	777.1	731.9
35°	595.1	626.4	645.8	669.7	680.8	723.6	759.6	781.2	777.1	757.3	716.3
37.5°	503.5	521.4	544.9	570.2	592.4	633.3	678.0	719.9	737.0	727.3	696.5
40°	415.5	436.7	464.8	485.5	500.7	541.7	597.0	642.6	679.9	685.9	667.0
42.5°	353.3	374.5	391.5	414.1	426.1	465.7	514.5	571.6	615.8	639.3	631.0
45°	305.4	318.3	332.1	345.0	359.7	394.7	439.9	502.5	552.3	585.4	588.7
47.5°	263.5	275.0	287.0	298.9	307.2	334.4	375.9	427.0	481.3	526.9	544.9
50°	234.0	239.5	248.3	255.2	264.9	288.3	321.5	365.7	423.3	472.6	496.1
52.5°	205.0	211.9	218.8	224.8	231.2	247.8	278.2	316.4	366.2	416.9	445.9
55°	180.6	186.1	192.5	196.7	200.4	215.1	238.1	267.6	310.5	358.4	394.3
57.5°	160.8	163.1	168.6	170.9	175.0	187.0	203.6	229.8	264.4	310.9	340.4
60°	139.1	143.7	147.9	149.7	152.9	161.2	172.7	197.1	227.1	261.2	294.8
62.5°	121.6	123.4	126.7	129.0	131.3	140.0	149.7	168.1	190.7	219.3	250.1
65°	105.5	106.4	108.2	111.5	112.9	119.3	124.8	138.2	159.4	181.0	211.9
67.5°	88.9	89.8	92.1	94.0	95.3	99.5	105.5	115.2	126.7	150.6	167.7
70°	76.0	76.0	77.4	78.3	79.7	81.5	84.8	92.1	102.7	117.9	133.6
72.5°	63.6	63.6	63.6	64.9	64.9	66.3	68.2	73.2	80.6	92.6	102.7
75°	49.3	49.7	50.7	50.7	51.1	53.0	54.4	55.7	59.4	67.2	76.5
77.5°	37.3	38.2	38.7	37.8	38.7	38.7	40.5	42.4	44.2	46.5	53.4
80°	27.6	28.1	27.2	27.6	27.6	28.6	29.5	29.0	29.9	32.7	34.5
82.5°	18.4	18.9	18.9	18.9	18.9	20.3	20.3	19.8	20.3	20.7	21.2
85°	11.5	11.1	11.1	11.5	11.1	11.1	11.5	12.0	11.5	12.0	12.4
87.5°	5.1	5.1	5.1	5.1	4.6	4.6	5.1	4.6	5.1	4.6	4.1
90°	12.6	12.0	11.4	11.4	11.4	10.9	10.3	9.7	10.3	9.1	8.0
92.5°	54.3	58.3	66.9	74.1	81.2	102.9	137.7	186.3	224.0	196.0	142.3
95°	157.2	174.9	202.9	230.6	258.3	334.9	423.5	479.0	465.8	351.5	214.9
97.5°	365.8	400.1	439.0	471.0	503.0	565.8	609.8	600.7	498.4	336.6	196.0
100°	545.8	580.7	630.4	651.6	672.7	700.7	689.3	605.8	459.5	298.4	181.8
102.5°	710.4	733.3	759.0	764.8	770.5	753.3	685.3	563.0	410.9	272.6	177.8
105°	815.6	820.2	819.0	807.3	795.6	739.0	640.1	509.3	374.9	260.1	180.0
107.5°	853.9	843.6	818.5	794.5	770.5	691.6	584.7	465.2	351.5	256.6	186.9
110°	844.8	820.8	780.2	748.8	717.3	634.4	535.5	433.8	340.6	257.8	194.9

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	801.9	771.6	724.2	692.8	661.3	584.1	499.5	416.1	335.5	261.2	203.5
115°	749.3	715.0	669.9	642.4	615.0	548.1	477.8	406.4	334.4	265.8	212.6
117.5°	696.7	667.0	627.0	603.0	579.0	524.7	465.2	401.2	333.8	270.3	221.8
120°	654.4	629.3	596.7	576.4	556.1	510.4	457.2	397.2	333.8	275.5	231.5
122.5°	623.0	602.4	576.1	559.0	541.8	501.3	450.4	392.7	333.2	280.6	240.6
125°	601.8	585.3	562.4	546.7	531.0	491.5	442.4	387.5	332.6	285.8	249.8
127.5°	587.6	572.7	549.8	535.0	520.1	480.7	433.2	380.7	331.5	289.8	257.8
130°	573.8	559.6	536.1	521.0	505.8	467.0	421.8	374.4	330.9	294.4	265.2
132.5°	559.0	542.4	519.5	504.4	489.3	451.5	409.8	368.7	330.4	298.4	272.6
135°	538.4	522.4	499.5	485.2	471.0	436.1	398.9	362.9	329.8	302.4	278.9
137.5°	516.1	499.5	477.8	464.6	451.5	421.2	388.7	357.8	329.8	304.6	283.5
140°	489.3	476.7	456.7	444.7	432.7	406.9	380.1	353.8	329.2	307.5	288.1
142.5°	464.7	453.2	436.1	426.1	416.1	394.9	372.1	350.4	329.2	309.8	291.5
145°	441.2	431.5	417.2	409.2	401.2	384.1	364.7	346.4	328.1	310.4	293.8
147.5°	421.2	412.7	401.8	395.2	388.7	374.4	358.4	342.9	326.4	310.9	296.1
150°	404.1	396.7	387.5	382.4	377.2	365.8	352.6	338.9	324.6	310.9	297.8
152.5°	388.7	382.9	375.5	371.5	367.5	357.2	346.4	334.4	321.8	309.8	298.9
155°	374.9	370.4	364.7	361.2	357.8	349.2	340.1	329.8	318.9	308.6	299.5
157.5°	362.4	358.9	354.4	351.5	348.6	341.2	333.2	325.2	316.1	307.5	299.5
160°	350.9	347.5	344.1	341.8	339.5	333.2	326.9	320.1	312.6	305.8	299.5
162.5°	340.1	336.6	334.4	332.4	330.4	325.8	320.6	315.5	309.2	304.1	299.5
165°	329.8	327.5	325.2	323.8	322.4	318.4	314.9	310.4	305.8	301.8	298.4
167.5°	320.1	318.4	317.2	316.4	315.5	312.1	309.2	305.8	302.4	299.5	297.2
170°	311.5	310.9	309.8	309.0	308.1	305.8	304.1	301.2	298.9	297.2	296.1
172.5°	304.1	303.5	302.9	302.4	301.8	300.6	299.5	297.2	295.5	294.9	294.9
175°	298.4	297.2	297.2	297.2	297.2	296.1	295.5	294.4	293.2	293.2	293.8
177.5°	293.8	293.2	293.8	293.5	293.2	293.2	292.6	292.1	291.5	291.5	292.6
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	586.4	584.1	582.7	582.2	578.1	575.8	574.4	573.5	572.1	568.4	565.2
5°	608.5	602.0	598.8	595.1	588.7	581.3	575.3	571.6	567.0	559.6	552.7
7.5°	629.2	619.5	613.1	608.0	597.0	585.0	575.3	567.5	558.7	548.6	538.9
10°	650.9	635.2	626.9	619.1	602.9	587.3	573.5	562.0	549.5	536.2	525.6
12.5°	667.9	647.2	638.0	626.9	607.1	588.7	571.2	555.5	539.4	525.1	509.9
15°	687.7	661.9	651.3	637.0	609.9	585.9	563.3	546.3	529.7	508.5	492.4
17.5°	699.2	669.3	654.1	641.6	612.2	583.1	556.9	535.7	516.4	495.2	478.1
20°	710.7	676.6	659.6	642.1	607.1	576.2	548.6	523.3	503.0	480.0	462.5
22.5°	714.4	674.8	656.8	640.7	603.9	569.3	537.5	511.7	488.3	465.2	445.4
25°	714.4	674.3	653.2	632.4	593.7	558.3	526.5	498.4	472.1	449.1	429.3
27.5°	707.0	665.1	643.0	624.1	584.1	545.8	513.1	482.3	456.9	433.9	411.3
30°	697.8	651.8	629.7	607.1	568.4	532.0	496.5	468.0	441.3	415.0	394.7
32.5°	686.3	637.5	613.1	590.0	549.1	511.3	478.6	450.5	425.1	398.0	375.4
35°	669.7	616.3	589.1	568.9	529.2	490.1	458.8	431.1	406.7	378.6	354.2
37.5°	648.5	597.0	569.3	544.4	503.5	467.5	438.0	411.3	387.4	361.6	334.4
40°	623.7	569.8	545.8	519.6	476.3	442.2	414.6	390.6	366.7	342.2	316.0
42.5°	595.6	542.1	515.4	490.1	448.6	415.0	389.2	367.6	345.5	322.9	294.8
45°	562.0	511.7	486.0	462.0	421.9	387.4	363.9	343.2	324.3	301.2	276.4
47.5°	524.2	480.4	454.2	428.4	389.2	359.3	336.2	318.7	302.6	279.6	257.0
50°	487.3	444.0	422.8	396.6	360.7	332.6	309.1	294.3	281.9	259.3	239.1
52.5°	440.8	408.1	387.8	365.3	330.7	302.2	283.7	270.8	256.1	238.6	220.6
55°	399.8	369.4	353.3	332.1	298.0	272.7	257.0	245.0	233.5	217.9	203.6
57.5°	353.3	334.4	318.3	299.9	266.2	244.6	230.8	220.6	210.0	197.1	185.6
60°	304.5	295.7	280.1	265.3	236.8	217.9	206.4	197.1	187.0	176.4	166.7
62.5°	261.2	256.1	246.9	235.4	208.7	192.5	181.0	174.1	166.7	157.1	147.9
65°	220.2	217.9	209.1	200.8	182.4	168.1	158.0	153.8	145.6	138.2	129.9
67.5°	183.8	181.0	176.0	172.3	156.6	143.3	138.2	132.7	125.7	120.2	113.3
70°	146.9	146.5	143.3	138.6	130.4	120.7	115.6	111.9	105.0	100.9	95.8
72.5°	114.2	116.5	113.8	111.9	106.4	99.5	94.9	92.6	87.1	83.8	80.1
75°	85.2	87.1	88.4	85.2	83.8	80.6	76.5	74.2	71.4	66.8	65.4
77.5°	58.0	62.2	62.2	63.1	63.6	61.7	58.5	56.7	53.4	52.5	50.7
80°	38.2	41.9	42.4	43.3	44.7	44.7	42.4	41.9	38.7	38.2	36.8
82.5°	22.1	25.3	27.2	28.6	28.1	29.9	28.1	27.6	25.8	25.8	24.9
85°	12.0	12.4	13.4	14.3	15.2	16.1	16.1	15.7	15.2	14.7	13.8
87.5°	4.6	4.6	5.1	4.6	5.1	6.0	6.4	6.4	6.0	5.5	4.6
90°	8.0	4.6	4.6	4.6	4.0	3.4	1.7	0.6	1.7	3.4	4.0
92.5°	86.9	51.4	44.0	36.6	26.3	17.7	11.4	8.0	11.4	17.7	26.3
95°	121.2	71.4	59.4	47.4	33.7	26.3	20.6	18.9	20.6	26.3	33.7
97.5°	115.5	76.0	65.7	55.4	43.4	36.6	31.4	31.4	31.4	36.6	43.4
100°	117.2	83.4	74.3	65.2	54.3	47.4	43.4	43.4	43.4	47.4	54.3
102.5°	122.9	93.2	84.6	76.0	65.7	59.4	56.0	54.9	56.0	59.4	65.7
105°	132.6	105.2	96.9	88.6	78.3	71.4	68.6	66.9	68.6	71.4	78.3
107.5°	142.9	117.7	109.4	101.2	91.4	84.0	81.2	80.0	81.2	84.0	91.4
110°	154.9	129.7	122.0	114.3	104.0	97.2	94.3	93.2	94.3	97.2	104.0

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	166.3	142.3	134.6	126.9	116.6	110.3	106.9	105.7	106.9	110.3	116.6
115°	178.3	155.5	147.8	140.0	129.2	123.5	119.5	117.7	119.5	123.5	129.2
117.5°	189.8	168.0	160.0	152.0	141.7	135.5	132.0	130.3	132.0	135.5	141.7
120°	201.8	180.0	172.0	164.0	154.3	148.0	144.0	142.9	144.0	148.0	154.3
122.5°	213.2	191.5	183.8	176.0	165.2	159.5	155.5	154.3	155.5	159.5	165.2
125°	223.5	202.9	194.9	186.9	176.0	169.8	166.3	164.0	166.3	169.8	176.0
127.5°	233.2	213.2	205.2	197.2	185.8	178.9	174.9	173.2	174.9	178.9	185.8
130°	242.9	223.5	215.2	206.9	196.0	187.5	182.9	180.6	182.9	187.5	196.0
132.5°	250.9	231.5	223.8	216.0	204.0	196.0	189.8	188.0	189.8	196.0	204.0
135°	258.3	239.5	232.0	224.6	212.6	202.9	197.2	194.9	197.2	202.9	212.6
137.5°	264.1	246.3	239.2	232.1	219.5	210.3	204.0	201.8	204.0	210.3	219.5
140°	269.8	252.6	245.8	238.9	226.9	217.2	210.9	209.2	210.9	217.2	226.9
142.5°	274.9	258.3	251.8	245.2	233.8	224.6	218.9	217.2	218.9	224.6	233.8
145°	278.3	263.5	257.2	250.9	240.1	232.1	226.3	224.6	226.3	232.1	240.1
147.5°	282.3	268.1	262.4	256.6	247.5	238.9	233.8	233.2	233.8	238.9	247.5
150°	285.2	272.6	267.2	261.8	253.2	246.3	241.8	241.2	241.8	246.3	253.2
152.5°	287.5	276.6	271.8	266.9	259.5	253.2	248.6	248.6	248.6	253.2	259.5
155°	289.8	280.1	275.8	271.5	265.2	259.5	256.1	255.5	256.1	259.5	265.2
157.5°	291.5	282.9	279.5	276.1	270.3	265.8	262.3	262.3	262.3	265.8	270.3
160°	292.6	285.8	282.6	279.5	274.9	270.9	268.6	268.6	268.6	270.9	274.9
162.5°	293.8	287.5	285.2	282.9	278.9	275.5	273.8	274.3	273.8	275.5	278.9
165°	293.8	288.6	286.9	285.2	282.3	279.5	278.3	278.3	278.3	279.5	282.3
167.5°	293.8	289.8	288.4	286.9	285.2	282.9	282.3	282.9	282.3	282.9	285.2
170°	293.2	290.4	289.5	288.6	287.5	285.8	285.2	285.8	285.2	285.8	287.5
172.5°	292.6	290.9	290.4	289.8	289.2	288.1	288.1	288.6	288.1	288.1	289.2
175°	292.1	290.9	290.9	290.9	290.4	289.8	289.8	290.4	289.8	289.8	290.4
177.5°	291.5	290.9	290.9	290.9	290.9	290.4	290.9	291.5	290.9	290.4	290.9
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	562.4	561.5	560.6	556.9	553.7	548.1	543.5	541.7	541.2	541.7	540.3
5°	546.3	545.8	542.6	536.2	530.2	523.7	519.1	514.5	511.7	511.7	508.5
7.5°	531.1	527.9	525.1	516.8	509.9	501.2	494.2	490.1	487.8	482.7	482.7
10°	515.0	510.4	506.7	498.8	488.7	480.0	471.2	466.1	462.0	458.3	456.9
12.5°	498.8	495.2	488.3	480.0	469.8	458.8	449.6	445.9	436.2	428.4	428.8
15°	483.6	475.4	472.1	460.2	448.2	437.6	424.2	413.6	405.8	400.7	394.3
17.5°	466.6	458.3	452.3	442.2	426.5	409.9	397.1	382.8	374.9	366.2	362.0
20°	447.7	440.8	436.2	420.1	401.2	381.4	367.1	358.4	349.6	343.2	339.5
22.5°	431.6	422.8	417.3	395.7	374.9	355.1	344.1	336.7	329.3	323.8	322.0
25°	410.9	405.8	392.4	373.6	348.2	334.9	325.2	315.5	311.4	307.7	303.5
27.5°	393.8	381.4	372.2	347.3	331.6	316.4	306.8	299.4	294.3	290.6	287.4
30°	372.6	361.1	348.2	327.5	313.2	298.9	290.2	284.2	278.7	276.4	273.6
32.5°	350.5	339.9	327.5	310.9	293.4	282.4	275.4	269.0	265.3	263.0	259.8
35°	330.7	317.4	309.1	293.4	279.1	266.7	260.2	254.7	250.6	249.7	249.2
37.5°	309.5	299.4	291.6	275.4	263.5	252.9	246.9	240.9	238.6	238.1	236.3
40°	291.1	282.4	275.0	259.8	246.9	237.2	232.6	228.9	226.6	226.6	226.2
42.5°	275.0	265.8	258.4	244.6	233.1	224.3	219.3	215.6	214.6	215.1	214.6
45°	257.0	249.2	241.8	227.5	217.9	211.4	205.9	204.1	202.7	203.1	203.6
47.5°	240.0	233.5	226.2	214.6	203.6	196.7	193.5	191.6	191.6	191.6	192.5
50°	224.8	217.4	211.0	199.0	188.9	183.3	180.6	178.3	178.7	179.2	179.6
52.5°	206.8	200.4	195.8	183.8	176.4	169.5	166.3	166.7	166.3	166.3	167.2
55°	191.2	184.7	180.1	169.0	161.7	157.1	154.3	152.9	153.4	152.5	154.3
57.5°	173.7	168.1	164.9	154.3	147.9	143.7	141.4	139.1	140.0	139.6	139.1
60°	158.5	152.0	146.9	139.6	134.0	129.0	127.6	125.3	126.2	125.3	124.8
62.5°	140.9	135.9	132.2	124.8	120.2	116.1	112.9	111.5	111.0	109.6	108.2
65°	123.4	120.7	117.0	109.6	105.0	101.8	100.0	98.6	98.1	94.4	90.3
67.5°	107.3	105.5	101.8	96.3	92.1	88.9	86.1	83.8	81.1	78.3	76.0
70°	92.1	89.4	87.1	82.0	78.3	75.1	72.3	69.6	68.2	65.4	64.5
72.5°	77.4	74.6	72.3	67.7	64.5	61.3	60.3	57.1	55.7	55.3	55.3
75°	62.2	59.9	58.5	54.4	51.6	49.3	47.9	47.0	46.1	45.1	43.8
77.5°	47.4	46.1	45.1	42.4	40.1	38.7	38.2	35.0	34.1	33.2	32.2
80°	34.5	34.1	33.2	30.9	29.9	26.7	26.7	25.8	25.3	25.3	25.3
82.5°	23.5	22.6	22.1	19.8	19.3	18.9	18.4	18.0	18.4	18.0	18.4
85°	12.4	12.0	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.1	11.5
87.5°	4.6	4.6	4.6	4.6	4.1	4.6	4.6	4.1	4.6	4.6	4.6
90°	4.6	4.6	4.6	8.0	8.0	9.1	10.3	9.7	10.3	10.9	11.4
92.5°	36.6	44.0	51.4	86.9	142.3	196.0	224.0	186.3	137.7	102.9	81.2
95°	47.4	59.4	71.4	121.2	214.9	351.5	465.8	479.0	423.5	334.9	258.3
97.5°	55.4	65.7	76.0	115.5	196.0	336.6	498.4	600.7	609.8	565.8	503.0
100°	65.2	74.3	83.4	117.2	181.8	298.4	459.5	605.8	689.3	700.7	672.7
102.5°	76.0	84.6	93.2	122.9	177.8	272.6	410.9	563.0	685.3	753.3	770.5
105°	88.6	96.9	105.2	132.6	180.0	260.1	374.9	509.3	640.1	739.0	795.6
107.5°	101.2	109.4	117.7	142.9	186.9	256.6	351.5	465.2	584.7	691.6	770.5
110°	114.3	122.0	129.7	154.9	194.9	257.8	340.6	433.8	535.5	634.4	717.3

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	126.9	134.6	142.3	166.3	203.5	261.2	335.5	416.1	499.5	584.1	661.3
115°	140.0	147.8	155.5	178.3	212.6	265.8	334.4	406.4	477.8	548.1	615.0
117.5°	152.0	160.0	168.0	189.8	221.8	270.3	333.8	401.2	465.2	524.7	579.0
120°	164.0	172.0	180.0	201.8	231.5	275.5	333.8	397.2	457.2	510.4	556.1
122.5°	176.0	183.8	191.5	213.2	240.6	280.6	333.2	392.7	450.4	501.3	541.8
125°	186.9	194.9	202.9	223.5	249.8	285.8	332.6	387.5	442.4	491.5	531.0
127.5°	197.2	205.2	213.2	233.2	257.8	289.8	331.5	380.7	433.2	480.7	520.1
130°	206.9	215.2	223.5	242.9	265.2	294.4	330.9	374.4	421.8	467.0	505.8
132.5°	216.0	223.8	231.5	250.9	272.6	298.4	330.4	368.7	409.8	451.5	489.3
135°	224.6	232.0	239.5	258.3	278.9	302.4	329.8	362.9	398.9	436.1	471.0
137.5°	232.1	239.2	246.3	264.1	283.5	304.6	329.8	357.8	388.7	421.2	451.5
140°	238.9	245.8	252.6	269.8	288.1	307.5	329.2	353.8	380.1	406.9	432.7
142.5°	245.2	251.8	258.3	274.9	291.5	309.8	329.2	350.4	372.1	394.9	416.1
145°	250.9	257.2	263.5	278.3	293.8	310.4	328.1	346.4	364.7	384.1	401.2
147.5°	256.6	262.4	268.1	282.3	296.1	310.9	326.4	342.9	358.4	374.4	388.7
150°	261.8	267.2	272.6	285.2	297.8	310.9	324.6	338.9	352.6	365.8	377.2
152.5°	266.9	271.8	276.6	287.5	298.9	309.8	321.8	334.4	346.4	357.2	367.5
155°	271.5	275.8	280.1	289.8	299.5	308.6	318.9	329.8	340.1	349.2	357.8
157.5°	276.1	279.5	282.9	291.5	299.5	307.5	316.1	325.2	333.2	341.2	348.6
160°	279.5	282.6	285.8	292.6	299.5	305.8	312.6	320.1	326.9	333.2	339.5
162.5°	282.9	285.2	287.5	293.8	299.5	304.1	309.2	315.5	320.6	325.8	330.4
165°	285.2	286.9	288.6	293.8	298.4	301.8	305.8	310.4	314.9	318.4	322.4
167.5°	286.9	288.4	289.8	293.8	297.2	299.5	302.4	305.8	309.2	312.1	315.5
170°	288.6	289.5	290.4	293.2	296.1	297.2	298.9	301.2	304.1	305.8	308.1
172.5°	289.8	290.4	290.9	292.6	294.9	294.9	295.5	297.2	299.5	300.6	301.8
175°	290.9	290.9	290.9	292.1	293.8	293.2	293.2	294.4	295.5	296.1	297.2
177.5°	290.9	290.9	290.9	291.5	292.6	291.5	291.5	292.1	292.6	293.2	293.2
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	540.3	542.1	539.8	541.2	538.0	537.5	538.0	538.0	538.5	538.9	539.4
5°	509.9	509.4	506.7	504.8	503.5	504.8	505.8	506.7	505.8	506.7	507.1
7.5°	481.3	480.0	478.6	475.4	476.3	475.4	478.1	476.7	476.7	479.0	480.9
10°	456.0	453.2	452.3	448.6	445.9	445.4	448.6	450.0	451.4	452.3	456.0
12.5°	423.3	419.2	415.9	417.3	409.5	412.7	413.6	411.8	417.3	423.8	420.1
15°	388.3	388.8	382.3	380.0	373.6	375.4	375.9	380.5	385.1	384.6	390.1
17.5°	362.5	359.7	354.2	353.8	351.0	352.4	351.9	355.6	354.2	356.5	361.1
20°	338.6	336.7	332.1	330.3	331.2	330.3	330.7	331.2	332.6	337.6	336.7
22.5°	319.7	317.4	317.4	315.1	312.3	311.4	313.7	315.1	316.9	317.8	320.1
25°	303.1	301.2	298.9	297.6	295.3	295.7	297.1	298.9	300.3	302.2	304.0
27.5°	286.0	286.0	283.7	283.3	282.4	281.9	283.7	284.7	284.7	286.0	287.9
30°	272.7	272.7	270.4	269.9	269.5	269.5	270.8	271.3	271.8	273.1	274.1
32.5°	259.8	259.3	258.4	258.9	258.4	258.9	258.9	259.3	260.2	260.7	262.6
35°	247.8	248.3	247.4	247.4	246.9	247.4	248.3	248.7	249.2	250.1	250.1
37.5°	236.3	237.2	236.8	238.1	238.1	238.1	238.1	239.1	239.1	239.1	238.6
40°	226.2	226.2	225.7	226.6	227.5	227.5	228.0	228.0	228.5	228.5	228.0
42.5°	214.6	215.6	217.0	217.4	218.3	217.9	219.3	218.8	219.3	218.3	217.4
45°	204.1	204.1	205.9	207.7	208.2	208.2	208.2	209.1	208.2	206.8	206.4
47.5°	192.5	193.5	194.4	196.7	197.1	197.1	197.1	197.1	196.2	196.2	196.2
50°	181.0	181.5	181.9	182.9	184.2	183.8	183.8	183.8	185.6	183.8	184.2
52.5°	167.2	167.7	168.1	170.0	169.5	169.5	170.0	170.0	171.3	170.9	170.0
55°	153.4	153.4	154.3	154.3	154.3	155.2	155.7	156.6	156.1	156.6	157.1
57.5°	139.6	138.6	138.2	138.2	139.6	139.1	139.6	139.6	141.4	142.3	142.8
60°	123.4	123.4	123.0	120.2	120.2	119.8	121.1	122.1	123.0	127.1	126.7
62.5°	106.9	105.0	103.2	103.6	100.9	102.3	101.3	102.3	105.0	108.2	108.7
65°	90.3	88.9	87.1	86.6	85.7	87.1	86.6	87.1	88.4	90.3	92.6
67.5°	75.5	75.1	74.2	73.7	73.7	73.7	74.6	74.6	75.1	76.5	77.8
70°	64.5	64.0	64.5	63.6	64.0	63.6	64.0	64.5	64.9	65.4	66.8
72.5°	54.4	54.4	54.4	53.4	54.4	53.9	53.9	54.4	54.8	55.3	56.2
75°	43.3	42.4	41.5	40.5	40.1	41.0	41.5	41.0	42.4	44.2	44.2
77.5°	32.7	32.2	32.2	32.2	32.7	32.2	33.2	32.7	33.2	33.2	34.1
80°	25.3	24.9	25.3	25.3	24.9	25.8	25.3	25.3	25.8	26.3	25.8
82.5°	18.4	18.9	18.4	18.4	18.4	19.3	18.4	18.4	18.4	18.9	18.9
85°	11.5	11.5	11.5	11.5	12.0	11.5	12.0	11.5	12.4	12.0	12.0
87.5°	4.1	4.6	5.1	5.1	5.1	5.1	4.6	5.1	5.5	5.1	5.5
90°	11.4	11.4	12.0	12.6	12.0	12.0	12.0	12.6	12.0	11.4	11.4
92.5°	74.1	66.9	58.3	54.3	52.0	52.0	52.0	54.3	58.3	66.9	74.1
95°	230.6	202.9	174.9	157.2	146.9	139.5	146.9	157.2	174.9	202.9	230.6
97.5°	471.0	439.0	400.1	365.8	348.6	334.9	348.6	365.8	400.1	439.0	471.0
100°	651.6	630.4	580.7	545.8	528.7	524.1	528.7	545.8	580.7	630.4	651.6
102.5°	764.8	759.0	733.3	710.4	692.2	688.7	692.2	710.4	733.3	759.0	764.8
105°	807.3	819.0	820.2	815.6	807.6	804.2	807.6	815.6	820.2	819.0	807.3
107.5°	794.5	818.5	843.6	853.9	858.5	859.0	858.5	853.9	843.6	818.5	794.5
110°	748.8	780.2	820.8	844.8	855.0	860.2	855.0	844.8	820.8	780.2	748.8

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	692.8	724.2	771.6	801.9	817.3	826.5	817.3	801.9	771.6	724.2	692.8
115°	642.4	669.9	715.0	749.3	767.6	772.2	767.6	749.3	715.0	669.9	642.4
117.5°	603.0	627.0	667.0	696.7	716.2	719.0	716.2	696.7	667.0	627.0	603.0
120°	576.4	596.7	629.3	654.4	669.3	675.6	669.3	654.4	629.3	596.7	576.4
122.5°	559.0	576.1	602.4	623.0	635.0	641.3	635.0	623.0	602.4	576.1	559.0
125°	546.7	562.4	585.3	601.8	612.7	616.1	612.7	601.8	585.3	562.4	546.7
127.5°	535.0	549.8	572.7	587.6	596.7	600.1	596.7	587.6	572.7	549.8	535.0
130°	521.0	536.1	559.6	573.8	583.0	586.4	583.0	573.8	559.6	536.1	521.0
132.5°	504.4	519.5	542.4	559.0	567.6	571.0	567.6	559.0	542.4	519.5	504.4
135°	485.2	499.5	522.4	538.4	547.5	551.0	547.5	538.4	522.4	499.5	485.2
137.5°	464.6	477.8	499.5	516.1	523.5	527.5	523.5	516.1	499.5	477.8	464.6
140°	444.7	456.7	476.7	489.3	497.3	501.8	497.3	489.3	476.7	456.7	444.7
142.5°	426.1	436.1	453.2	464.7	471.5	474.4	471.5	464.7	453.2	436.1	426.1
145°	409.2	417.2	431.5	441.2	447.0	449.8	447.0	441.2	431.5	417.2	409.2
147.5°	395.2	401.8	412.7	421.2	425.8	427.0	425.8	421.2	412.7	401.8	395.2
150°	382.4	387.5	396.7	404.1	407.5	408.1	407.5	404.1	396.7	387.5	382.4
152.5°	371.5	375.5	382.9	388.7	390.4	390.9	390.4	388.7	382.9	375.5	371.5
155°	361.2	364.7	370.4	374.9	376.7	376.7	376.7	374.9	370.4	364.7	361.2
157.5°	351.5	354.4	358.9	362.4	363.5	363.5	363.5	362.4	358.9	354.4	351.5
160°	341.8	344.1	347.5	350.9	351.5	351.5	351.5	350.9	347.5	344.1	341.8
162.5°	332.4	334.4	336.6	340.1	340.6	340.1	340.6	340.1	336.6	334.4	332.4
165°	323.8	325.2	327.5	329.8	329.2	328.6	329.2	329.8	327.5	325.2	323.8
167.5°	316.4	317.2	318.4	320.1	320.1	319.5	320.1	320.1	318.4	317.2	316.4
170°	309.0	309.8	310.9	311.5	310.9	310.9	310.9	311.5	310.9	309.8	309.0
172.5°	302.4	302.9	303.5	304.1	303.5	302.4	303.5	304.1	303.5	302.9	302.4
175°	297.2	297.2	297.2	298.4	297.2	296.1	297.2	298.4	297.2	297.2	297.2
177.5°	293.5	293.8	293.2	293.8	292.6	291.5	292.6	293.8	293.2	293.8	293.5
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6	571.6
2.5°	541.2	543.5	542.6	539.4	540.8	543.5	546.3	550.0	552.3	554.1	555.0
5°	509.4	513.6	512.7	512.7	514.5	519.1	523.7	531.6	534.3	537.5	542.1
7.5°	481.3	484.6	487.3	488.3	491.0	497.0	503.0	511.7	518.7	522.3	525.1
10°	456.5	458.8	462.9	465.2	468.0	475.4	484.1	493.3	500.2	506.7	510.4
12.5°	424.7	433.9	439.4	443.1	446.8	457.9	464.8	474.9	483.2	489.2	494.7
15°	389.2	400.3	403.5	417.8	427.0	435.7	446.3	458.3	466.1	473.1	480.4
17.5°	359.3	367.1	370.8	386.0	393.8	407.6	422.8	438.0	450.0	455.1	462.5
20°	340.4	344.5	351.9	357.0	365.3	381.4	398.0	416.4	434.4	439.4	446.8
22.5°	321.0	326.6	331.6	338.6	345.0	356.1	372.6	392.9	412.3	421.5	430.2
25°	303.5	309.1	312.3	319.7	325.7	336.7	348.2	369.0	392.0	399.8	413.6
27.5°	289.7	293.0	298.5	301.7	308.6	318.7	329.3	345.0	367.6	380.9	394.3
30°	275.9	278.2	282.8	287.4	292.5	299.4	311.4	326.6	347.3	358.8	372.2
32.5°	262.1	265.8	268.5	271.8	277.3	285.6	293.9	308.6	325.2	338.1	351.5
35°	250.6	252.0	255.6	259.3	263.0	270.4	279.1	293.4	308.2	318.3	330.3
37.5°	238.1	240.4	243.2	244.6	250.6	255.2	264.4	275.4	293.0	299.4	311.4
40°	228.5	228.0	230.8	233.1	235.8	243.2	248.7	260.7	274.5	284.7	292.0
42.5°	216.5	216.5	217.4	220.2	223.9	228.5	234.9	245.0	259.3	266.7	275.4
45°	206.8	205.4	205.9	207.7	210.0	214.6	221.1	229.8	244.1	250.1	259.3
47.5°	195.3	193.9	193.9	195.8	197.6	200.8	205.9	216.0	227.5	235.4	242.3
50°	182.4	182.9	182.4	183.8	184.7	187.9	193.5	201.7	212.3	218.8	226.6
52.5°	170.4	169.5	169.0	170.0	171.8	174.1	180.1	187.5	197.6	204.1	211.0
55°	155.7	156.6	156.6	156.6	159.4	160.3	164.9	172.3	182.4	187.5	193.9
57.5°	142.3	141.9	142.8	142.3	144.6	147.9	151.5	157.1	167.2	172.3	178.3
60°	127.6	128.1	128.5	128.5	130.4	133.6	137.7	142.8	151.1	156.1	161.7
62.5°	109.6	111.9	114.2	115.2	117.9	120.2	123.0	128.5	135.9	139.6	144.6
65°	92.6	95.8	99.0	101.3	103.2	105.5	109.2	114.2	120.2	123.9	129.0
67.5°	77.8	80.1	84.3	86.6	90.3	93.0	95.3	99.5	106.9	108.2	112.4
70°	67.2	68.2	70.0	71.9	76.0	78.3	81.1	85.2	90.7	94.0	96.3
72.5°	56.7	57.1	58.0	59.9	61.7	64.5	67.7	71.4	76.5	77.8	81.1
75°	45.1	47.9	47.9	49.3	50.7	52.0	54.8	58.5	61.7	64.0	65.9
77.5°	33.6	35.0	35.9	38.2	40.1	41.5	43.3	46.1	47.9	49.7	51.1
80°	26.3	26.7	27.2	27.2	28.1	29.9	31.8	33.6	35.9	36.8	38.2
82.5°	19.3	19.3	19.3	20.3	20.7	21.2	21.2	22.1	24.4	25.3	26.7
85°	12.4	12.4	12.4	12.4	12.9	13.4	13.8	14.3	14.3	14.3	15.2
87.5°	5.1	6.0	5.5	6.0	6.0	6.0	6.0	6.4	6.4	6.9	6.9
90°	11.4	10.9	10.3	9.7	10.3	9.1	8.0	8.0	4.6	4.6	4.6
92.5°	81.2	102.9	137.7	186.3	224.0	196.0	142.3	86.9	51.4	44.0	36.6
95°	258.3	334.9	423.5	479.0	465.8	351.5	214.9	121.2	71.4	59.4	47.4
97.5°	503.0	565.8	609.8	600.7	498.4	336.6	196.0	115.5	76.0	65.7	55.4
100°	672.7	700.7	689.3	605.8	459.5	298.4	181.8	117.2	83.4	74.3	65.2
102.5°	770.5	753.3	685.3	563.0	410.9	272.6	177.8	122.9	93.2	84.6	76.0
105°	795.6	739.0	640.1	509.3	374.9	260.1	180.0	132.6	105.2	96.9	88.6
107.5°	770.5	691.6	584.7	465.2	351.5	256.6	186.9	142.9	117.7	109.4	101.2
110°	717.3	634.4	535.5	433.8	340.6	257.8	194.9	154.9	129.7	122.0	114.3

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	661.3	584.1	499.5	416.1	335.5	261.2	203.5	166.3	142.3	134.6	126.9
115°	615.0	548.1	477.8	406.4	334.4	265.8	212.6	178.3	155.5	147.8	140.0
117.5°	579.0	524.7	465.2	401.2	333.8	270.3	221.8	189.8	168.0	160.0	152.0
120°	556.1	510.4	457.2	397.2	333.8	275.5	231.5	201.8	180.0	172.0	164.0
122.5°	541.8	501.3	450.4	392.7	333.2	280.6	240.6	213.2	191.5	183.8	176.0
125°	531.0	491.5	442.4	387.5	332.6	285.8	249.8	223.5	202.9	194.9	186.9
127.5°	520.1	480.7	433.2	380.7	331.5	289.8	257.8	233.2	213.2	205.2	197.2
130°	505.8	467.0	421.8	374.4	330.9	294.4	265.2	242.9	223.5	215.2	206.9
132.5°	489.3	451.5	409.8	368.7	330.4	298.4	272.6	250.9	231.5	223.8	216.0
135°	471.0	436.1	398.9	362.9	329.8	302.4	278.9	258.3	239.5	232.0	224.6
137.5°	451.5	421.2	388.7	357.8	329.8	304.6	283.5	264.1	246.3	239.2	232.1
140°	432.7	406.9	380.1	353.8	329.2	307.5	288.1	269.8	252.6	245.8	238.9
142.5°	416.1	394.9	372.1	350.4	329.2	309.8	291.5	274.9	258.3	251.8	245.2
145°	401.2	384.1	364.7	346.4	328.1	310.4	293.8	278.3	263.5	257.2	250.9
147.5°	388.7	374.4	358.4	342.9	326.4	310.9	296.1	282.3	268.1	262.4	256.6
150°	377.2	365.8	352.6	338.9	324.6	310.9	297.8	285.2	272.6	267.2	261.8
152.5°	367.5	357.2	346.4	334.4	321.8	309.8	298.9	287.5	276.6	271.8	266.9
155°	357.8	349.2	340.1	329.8	318.9	308.6	299.5	289.8	280.1	275.8	271.5
157.5°	348.6	341.2	333.2	325.2	316.1	307.5	299.5	291.5	282.9	279.5	276.1
160°	339.5	333.2	326.9	320.1	312.6	305.8	299.5	292.6	285.8	282.6	279.5
162.5°	330.4	325.8	320.6	315.5	309.2	304.1	299.5	293.8	287.5	285.2	282.9
165°	322.4	318.4	314.9	310.4	305.8	301.8	298.4	293.8	288.6	286.9	285.2
167.5°	315.5	312.1	309.2	305.8	302.4	299.5	297.2	293.8	289.8	288.4	286.9
170°	308.1	305.8	304.1	301.2	298.9	297.2	296.1	293.2	290.4	289.5	288.6
172.5°	301.8	300.6	299.5	297.2	295.5	294.9	294.9	292.6	290.9	290.4	289.8
175°	297.2	296.1	295.5	294.4	293.2	293.2	293.8	292.1	290.9	290.9	290.9
177.5°	293.2	293.2	292.6	292.1	291.5	291.5	292.6	291.5	290.9	290.9	290.9
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	571.6	571.6	571.6	571.6
2.5°	558.7	561.5	566.1	572.5
5°	545.8	553.7	561.0	570.7
7.5°	534.3	543.5	553.7	567.5
10°	521.0	532.5	545.4	562.4
12.5°	505.3	521.4	536.2	554.6
15°	493.8	505.8	524.6	546.3
17.5°	477.7	493.8	512.7	537.1
20°	462.5	479.5	500.7	526.0
22.5°	446.3	465.7	486.9	514.0
25°	429.8	450.5	471.7	500.7
27.5°	414.6	433.4	457.4	486.9
30°	396.1	417.8	440.8	471.7
32.5°	378.2	400.7	424.2	455.1
35°	358.8	381.4	407.2	436.7
37.5°	339.9	364.8	388.3	416.9
40°	319.2	345.0	369.4	398.4
42.5°	298.9	325.7	350.1	374.9
45°	280.1	306.3	328.4	351.9
47.5°	262.1	285.6	308.2	329.3
50°	244.6	264.4	285.1	302.6
52.5°	226.2	245.0	261.6	277.3
55°	209.6	224.3	239.1	253.3
57.5°	189.8	204.5	217.4	228.5
60°	173.2	182.4	194.8	206.4
62.5°	154.3	164.9	174.6	181.9
65°	135.9	145.1	152.5	158.9
67.5°	120.2	125.7	131.3	138.2
70°	101.3	105.9	112.4	117.5
72.5°	85.2	88.9	92.1	98.1
75°	69.1	72.3	74.2	79.7
77.5°	53.4	56.7	58.0	61.3
80°	41.0	41.5	43.3	46.1
82.5°	28.1	29.0	29.5	31.8
85°	16.1	18.4	18.0	18.9
87.5°	6.9	7.4	8.3	9.2
90°	4.0	3.4	1.7	0.6
92.5°	26.3	17.7	11.4	8.0
95°	33.7	26.3	20.6	18.9
97.5°	43.4	36.6	31.4	31.4
100°	54.3	47.4	43.4	43.4
102.5°	65.7	59.4	56.0	54.9
105°	78.3	71.4	68.6	66.9
107.5°	91.4	84.0	81.2	80.0
110°	104.0	97.2	94.3	93.2

TEST NUMBER: P1026327

CATALOG NUMBER: S124RDIP-B350D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	116.6	110.3	106.9	105.7
115°	129.2	123.5	119.5	117.7
117.5°	141.7	135.5	132.0	130.3
120°	154.3	148.0	144.0	142.9
122.5°	165.2	159.5	155.5	154.3
125°	176.0	169.8	166.3	164.0
127.5°	185.8	178.9	174.9	173.2
130°	196.0	187.5	182.9	180.6
132.5°	204.0	196.0	189.8	188.0
135°	212.6	202.9	197.2	194.9
137.5°	219.5	210.3	204.0	201.8
140°	226.9	217.2	210.9	209.2
142.5°	233.8	224.6	218.9	217.2
145°	240.1	232.1	226.3	224.6
147.5°	247.5	238.9	233.8	233.2
150°	253.2	246.3	241.8	241.2
152.5°	259.5	253.2	248.6	248.6
155°	265.2	259.5	256.1	255.5
157.5°	270.3	265.8	262.3	262.3
160°	274.9	270.9	268.6	268.6
162.5°	278.9	275.5	273.8	274.3
165°	282.3	279.5	278.3	278.3
167.5°	285.2	282.9	282.3	282.9
170°	287.5	285.8	285.2	285.8
172.5°	289.2	288.1	288.1	288.6
175°	290.4	289.8	289.8	290.4
177.5°	290.9	290.4	290.9	291.5
180°	290.9	290.9	290.9	290.9

(END OF REPORT)