

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026345

Luminaire Tested: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026345
REPORT IS A COMBINATION OF REPORTS P999375 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D590UB50-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3429.0 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	38	36	35
3	80	71	64	59	73	65	59	54	54	50	46	44	40	38	34	32	30
4	74	63	56	50	67	58	51	46	48	43	39	39	36	33	30	28	26
5	68	56	49	43	61	52	45	40	43	38	34	35	31	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18
8	53	41	34	29	49	38	32	27	32	27	23	26	23	20	21	18	16
9	50	38	31	26	45	35	29	24	30	24	21	24	21	18	20	17	15
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4484	4484	4484	4484
5°	4484	5067	4491	3872
10°	4460	5841	4457	3368
15°	4407	6574	4407	2820
20°	4351	7127	4328	2483
25°	4283	7157	4264	2243
30°	4211	6086	4179	2077
35°	4109	4592	4057	1954
40°	3996	3328	3917	1858
45°	3808	2529	3714	1773
50°	3586	2044	3488	1648
55°	3345	1693	3235	1481
60°	3103	1431	2964	1232
65°	2800	1166	2710	979
70°	2521	946	2403	795
75°	2210	682	2055	583
80°	1822	451	1657	428
85°	1324	233	1099	233

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 5613 cd/sqm

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	1.6
10°-20°	160.8	4.7
20°-30°	251.9	7.3
30°-40°	279.7	8.2
40°-50°	247.8	7.2
50°-60°	193.1	5.6
60°-70°	126.3	3.7
70°-80°	62.0	1.8
80°-90°	16.2	0.5
90°-100°	202.8	5.9
100°-110°	423.4	12.3
110°-120°	376.4	11.0
120°-130°	316.8	9.2
130°-140°	264.3	7.7
140°-150°	201.8	5.9
150°-160°	141.9	4.1
160°-170°	83.4	2.4
170°-180°	27.1	0.8
0°-30°	465.9	13.6
0°-40°	745.6	21.7
0°-60°	1186.6	34.6
0°-90°	1391.1	40.6
90°-120°	1002.5	29.2
90°-150°	1785.4	52.1
90°-180°	2038.0	59.4
0°-180°	3429.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	550	550	550	550	550	
5°	549	635	550	486	549	52
15°	526	842	526	361	526	148
25°	482	908	479	284	482	222
35°	420	559	415	238	420	263
45°	338	286	330	200	338	261
55°	244	171	236	149	244	218
65°	153	100	148	84	153	152
75°	77	46	71	39	77	81
85°	18	11	15	11	18	21
90°	0	12	0	12	0	2
95°	18	134	18	134	18	20
105°	64	774	64	774	64	69
115°	113	743	113	743	113	112
125°	158	593	158	593	158	141
135°	188	530	188	530	188	145
145°	216	433	216	433	216	136
155°	246	362	246	362	246	113
165°	268	316	268	316	268	76
175°	279	285	279	285	279	27
180°	280	280	280	280	280	

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9
2.5°	550.8	555.6	558.3	560.5	564.9	566.7	570.2	571.1	574.7	574.2	572.9
5°	549.0	557.4	563.6	570.2	578.2	582.7	587.5	594.6	598.2	603.0	606.1
7.5°	545.9	557.4	567.6	577.8	590.6	597.7	603.9	615.0	624.3	632.3	641.1
10°	541.0	555.6	570.7	584.4	602.2	610.6	619.9	636.3	649.1	660.2	674.4
12.5°	533.5	553.9	570.7	589.3	611.9	623.4	635.8	655.3	670.4	688.6	706.3
15°	525.5	548.1	570.2	594.6	620.3	633.6	646.0	672.2	695.2	716.0	735.5
17.5°	516.6	541.4	565.8	592.8	623.9	640.3	654.9	686.3	711.6	738.6	758.1
20°	506.0	533.0	560.9	591.1	626.1	644.2	660.6	696.5	724.4	753.7	778.1
22.5°	494.5	523.7	554.3	587.1	623.4	643.4	662.4	701.0	733.3	760.3	793.1
25°	481.6	512.6	544.1	578.7	619.4	641.1	660.6	698.7	733.3	768.8	800.7
27.5°	468.3	500.2	533.0	569.4	611.0	632.3	654.4	691.2	731.5	770.1	802.4
30°	453.7	484.7	519.3	553.9	598.2	619.4	642.0	681.9	725.8	764.3	799.3
32.5°	437.8	469.7	502.5	538.3	581.8	604.8	625.6	670.8	715.6	753.7	786.5
35°	420.0	450.2	481.2	518.0	560.9	581.8	606.6	653.5	698.7	739.1	760.3
37.5°	401.0	429.8	458.6	494.9	536.1	561.4	585.8	633.2	681.0	708.0	719.1
40°	383.3	408.5	433.8	468.8	510.4	536.6	561.4	610.6	652.7	673.5	665.1
42.5°	360.7	386.8	409.4	441.8	483.8	508.2	533.5	584.4	618.5	627.0	606.1
45°	338.5	360.2	381.9	413.4	457.7	478.5	505.6	553.0	581.3	573.8	543.2
47.5°	316.8	334.5	354.9	385.5	425.4	450.2	475.4	516.6	536.6	525.9	483.4
50°	291.1	308.8	330.1	356.7	395.2	419.2	439.1	477.2	492.3	466.1	414.7
52.5°	266.7	282.2	300.4	325.2	362.0	383.7	405.4	438.2	443.1	413.0	358.9
55°	243.7	256.1	275.2	295.1	328.8	351.8	366.9	394.8	393.5	355.8	309.3
57.5°	219.8	231.3	244.1	265.0	296.9	314.1	330.5	354.9	342.1	310.2	264.1
60°	198.5	205.1	218.0	237.9	265.0	280.0	292.9	306.2	295.1	260.5	225.1
62.5°	175.0	182.6	191.9	207.8	231.7	245.9	255.2	261.0	249.5	222.9	190.5
65°	152.9	159.5	169.3	183.4	201.6	212.2	217.1	221.1	214.9	184.8	159.1
67.5°	132.9	137.4	146.2	155.5	175.0	177.7	184.3	186.1	173.7	150.6	130.3
70°	113.0	117.4	121.4	132.5	141.3	146.2	147.5	147.5	135.1	120.1	103.2
72.5°	94.4	97.0	101.0	108.6	113.4	117.0	118.7	116.5	105.0	92.6	80.2
75°	76.7	78.0	81.5	86.4	90.4	89.1	88.6	86.0	77.5	68.7	61.6
77.5°	58.9	59.8	63.8	65.1	65.1	66.5	64.7	62.0	54.9	48.3	45.2
80°	44.3	45.6	46.1	47.0	46.1	46.1	44.8	40.3	36.8	33.7	31.5
82.5°	30.6	31.5	31.9	30.6	31.5	30.1	27.9	24.8	22.6	22.2	21.3
85°	18.2	18.6	18.2	18.2	16.8	16.4	14.6	14.2	13.3	13.3	12.8
87.5°	8.9	8.4	7.5	6.6	6.6	6.2	6.6	5.8	6.6	6.2	5.8
90°	0.5	1.6	3.3	3.8	4.4	4.4	4.4	7.7	7.7	8.8	9.9
92.5°	7.7	11.0	17.0	25.3	35.2	42.4	49.5	83.6	136.9	188.6	215.5
95°	18.1	19.8	25.3	32.4	45.6	57.2	68.7	116.5	206.7	338.1	448.0
97.5°	30.2	30.2	35.2	41.8	53.3	63.2	73.1	111.0	188.6	323.8	479.4
100°	41.8	41.8	45.6	52.2	62.7	71.5	80.3	112.7	174.8	287.0	442.0
102.5°	52.8	53.9	57.2	63.2	73.1	81.4	89.6	118.2	171.0	262.2	395.2
105°	64.3	66.0	68.7	75.3	85.2	93.2	101.1	127.5	173.2	250.1	360.6
107.5°	77.0	78.1	80.8	88.0	97.3	105.2	113.2	137.4	179.8	246.8	338.1
110°	89.6	90.7	93.5	100.0	109.9	117.4	124.8	149.0	187.5	247.9	327.6

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	101.7	102.8	106.1	112.1	122.0	129.4	136.9	160.0	195.7	251.2	322.7
115°	113.2	114.9	118.7	124.2	134.7	142.1	149.5	171.5	204.5	255.6	321.6
117.5°	125.3	127.0	130.3	136.3	146.2	153.9	161.6	182.5	213.3	260.0	321.0
120°	137.4	138.5	142.4	148.4	157.8	165.5	173.2	194.1	222.6	265.0	321.0
122.5°	148.4	149.5	153.4	158.9	169.3	176.8	184.2	205.0	231.4	269.9	320.5
125°	157.8	160.0	163.3	169.3	179.8	187.4	195.1	214.9	240.2	274.9	319.9
127.5°	166.6	168.2	172.1	178.7	189.7	197.4	205.0	224.3	247.9	278.7	318.8
130°	173.7	175.9	180.3	188.6	199.0	207.0	214.9	233.6	255.1	283.1	318.3
132.5°	180.9	182.5	188.6	196.2	207.8	215.2	222.6	241.3	262.2	287.0	317.7
135°	187.5	189.7	195.1	204.5	216.0	223.2	230.3	248.5	268.3	290.8	317.2
137.5°	194.1	196.2	202.3	211.1	223.2	230.0	236.9	254.0	272.7	293.0	317.2
140°	201.2	202.8	208.9	218.2	229.8	236.4	243.0	259.5	277.1	295.7	316.6
142.5°	208.9	210.5	216.0	224.8	235.8	242.2	248.5	264.4	280.4	297.9	316.6
145°	216.0	217.7	223.2	230.9	241.3	247.4	253.4	267.7	282.6	298.5	315.5
147.5°	224.3	224.8	229.8	238.0	246.8	252.3	257.8	271.6	284.8	299.0	313.9
150°	232.0	232.5	236.9	243.5	251.8	257.0	262.2	274.3	286.4	299.0	312.2
152.5°	239.1	239.1	243.5	249.6	256.7	261.4	266.1	276.5	287.5	297.9	309.5
155°	245.7	246.3	249.6	255.1	261.1	265.2	269.4	278.7	288.1	296.8	306.7
157.5°	252.3	252.3	255.6	260.0	265.5	268.8	272.1	280.4	288.1	295.7	304.0
160°	258.4	258.4	260.6	264.4	268.8	271.8	274.9	281.5	288.1	294.1	300.7
162.5°	263.9	263.3	265.0	268.3	272.1	274.3	276.5	282.6	288.1	292.4	297.4
165°	267.7	267.7	268.8	271.6	274.3	276.0	277.6	282.6	287.0	290.3	294.1
167.5°	272.1	271.6	272.1	274.3	276.0	277.4	278.7	282.6	285.9	288.1	290.8
170°	274.9	274.3	274.9	276.5	277.6	278.5	279.3	282.0	284.8	285.9	287.5
172.5°	277.6	277.1	277.1	278.2	278.7	279.2	279.8	281.5	283.7	283.7	284.2
175°	279.3	278.7	278.7	279.3	279.8	279.8	279.8	280.9	282.6	282.0	282.0
177.5°	280.4	279.8	279.3	279.8	279.8	279.8	279.8	280.4	281.5	280.4	280.4
180°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9
2.5°	576.5	581.3	581.8	586.2	584.9	582.7	586.6	584.0	589.3	587.5	589.7
5°	610.1	616.8	622.5	626.1	632.3	631.0	637.6	635.4	640.3	635.4	641.6
7.5°	649.6	660.6	666.4	675.7	678.4	678.8	686.8	688.6	691.7	688.6	692.1
10°	688.1	701.4	714.7	722.2	727.1	733.7	740.8	743.9	746.2	743.1	745.3
12.5°	723.1	743.9	758.6	773.6	777.2	782.9	790.5	789.6	798.4	796.7	800.7
15°	755.5	778.5	796.2	808.2	817.9	822.8	837.0	837.9	837.4	841.9	839.2
17.5°	784.3	803.8	829.0	844.5	856.5	856.5	864.5	880.9	879.5	879.1	881.7
20°	807.7	829.9	853.4	879.5	889.3	891.0	902.1	910.5	911.9	911.9	911.9
22.5°	825.5	851.6	876.9	895.5	903.0	909.2	919.0	924.3	926.0	925.2	926.0
25°	834.3	859.1	884.8	901.7	906.1	909.7	910.5	913.6	913.2	907.9	911.0
27.5°	836.1	860.0	876.9	881.3	879.1	876.9	862.7	864.0	860.0	852.1	855.2
30°	828.1	841.0	840.5	826.8	822.8	813.5	800.7	781.6	766.1	759.4	761.7
32.5°	799.3	799.3	783.4	752.4	738.6	721.8	698.7	681.5	661.1	656.7	665.1
35°	759.4	736.8	707.6	666.8	646.0	633.6	593.7	581.3	564.0	559.2	563.2
37.5°	697.4	659.8	617.2	579.1	561.4	539.2	504.2	486.5	474.1	465.7	469.7
40°	627.9	582.2	537.9	490.9	471.4	453.3	427.1	411.2	391.2	392.1	393.5
42.5°	561.4	507.8	458.1	414.7	396.1	381.1	362.9	343.4	336.3	334.1	331.9
45°	490.9	433.8	387.3	354.9	338.1	323.9	307.1	296.0	287.6	285.8	288.0
47.5°	424.5	376.2	331.9	301.7	288.0	280.9	267.6	257.4	252.1	247.7	250.3
50°	364.2	319.0	283.6	258.3	248.6	243.7	231.3	226.0	220.7	219.3	218.9
52.5°	314.6	276.0	245.5	225.1	217.6	214.9	205.6	198.1	193.6	195.0	195.8
55°	269.4	236.6	212.7	196.3	190.1	187.0	180.3	175.0	171.9	170.6	171.5
57.5°	229.5	201.2	183.9	170.6	165.7	164.4	157.3	155.5	153.3	152.0	152.0
60°	193.2	173.2	157.3	149.8	144.4	143.1	137.8	135.6	135.1	133.8	132.9
62.5°	162.6	146.2	135.1	127.2	124.9	124.5	121.0	118.3	117.0	116.1	116.1
65°	136.0	124.1	114.8	109.0	107.2	106.3	102.4	101.5	100.6	99.7	99.3
67.5°	113.4	102.8	96.1	92.2	89.9	90.4	88.2	86.4	86.4	86.0	85.5
70°	91.7	85.1	79.3	77.1	76.2	75.3	74.4	73.1	72.7	72.7	72.7
72.5°	72.2	67.8	64.7	63.4	62.5	61.6	60.7	60.7	60.7	60.3	60.3
75°	55.4	53.6	51.4	50.1	50.1	51.0	49.6	48.3	47.0	46.1	46.5
77.5°	41.6	40.8	39.4	37.2	37.7	36.8	36.8	35.9	36.3	36.3	35.4
80°	30.6	29.2	28.8	27.5	27.9	27.5	27.0	27.0	26.1	26.1	26.1
82.5°	21.3	19.9	19.9	19.5	19.1	19.1	18.6	18.6	19.1	18.2	18.2
85°	12.8	12.4	12.4	11.5	11.5	11.5	11.5	12.0	11.5	11.1	11.1
87.5°	5.8	6.2	5.8	5.3	5.3	5.3	4.9	4.9	4.4	4.9	4.9
90°	9.3	9.9	10.4	11.0	11.0	11.0	11.5	12.1	11.5	11.5	11.5
92.5°	179.2	132.5	98.9	78.1	71.2	64.3	56.1	52.2	50.0	50.0	50.0
95°	460.7	407.3	322.1	248.5	221.8	195.1	168.2	151.2	141.3	134.1	141.3
97.5°	577.8	586.5	544.2	483.8	453.0	422.2	384.8	351.8	335.3	322.1	335.3
100°	582.7	663.0	674.0	647.0	626.6	606.3	558.5	525.0	508.5	504.1	508.5
102.5°	541.5	659.1	724.5	741.0	735.5	730.0	705.3	683.3	665.7	662.4	665.7
105°	489.8	615.7	710.8	765.2	776.4	787.7	788.8	784.4	776.8	773.5	776.8
107.5°	447.5	562.4	665.2	741.0	764.1	787.2	811.4	821.3	825.7	826.2	825.7
110°	417.2	515.1	610.2	689.9	720.2	750.4	789.4	812.5	822.4	827.3	822.4

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	400.2	480.5	561.8	636.0	666.2	696.5	742.1	771.3	786.1	794.9	786.1
115°	390.8	459.6	527.2	591.5	617.9	644.3	687.7	720.7	738.3	742.7	738.3
117.5°	385.9	447.5	504.6	556.9	580.0	603.0	641.5	670.1	688.8	691.5	688.8
120°	382.1	439.8	490.9	534.9	554.4	573.9	605.2	629.4	643.7	649.8	643.7
122.5°	377.7	433.2	482.1	521.1	537.6	554.1	579.4	599.2	610.7	616.8	610.7
125°	372.7	425.5	472.8	510.7	525.8	540.9	562.9	578.9	589.3	592.6	589.3
127.5°	366.1	416.7	462.3	500.2	514.5	528.8	550.8	565.1	573.9	577.2	573.9
130°	360.1	405.7	449.1	486.5	501.0	515.6	538.2	551.9	560.7	564.0	560.7
132.5°	354.6	394.1	434.3	470.6	485.2	499.7	521.7	537.6	545.9	549.2	545.9
135°	349.1	383.7	419.4	453.0	466.8	480.5	502.4	517.8	526.6	529.9	526.6
137.5°	344.1	373.8	405.1	434.3	447.0	459.6	480.5	496.4	503.5	507.4	503.5
140°	340.3	365.6	391.4	416.1	427.6	439.2	458.5	470.6	478.3	482.7	478.3
142.5°	337.0	357.9	379.9	400.2	409.8	419.4	435.9	446.9	453.5	456.3	453.5
145°	333.1	350.7	369.4	385.9	393.6	401.3	415.0	424.4	429.9	432.6	429.9
147.5°	329.8	344.7	360.1	373.8	380.2	386.5	396.9	405.1	409.5	410.6	409.5
150°	326.0	339.2	351.8	362.8	367.8	372.7	381.5	388.7	391.9	392.5	391.9
152.5°	321.6	333.1	343.6	353.5	357.4	361.2	368.3	373.8	375.5	376.0	375.5
155°	317.2	327.1	335.9	344.1	347.4	350.7	356.2	360.6	362.3	362.3	362.3
157.5°	312.8	320.5	328.2	335.3	338.0	340.8	345.2	348.5	349.6	349.6	349.6
160°	307.8	314.4	320.5	326.5	328.7	330.9	334.2	337.5	338.1	338.1	338.1
162.5°	303.4	308.4	313.3	317.7	319.6	321.6	323.8	327.1	327.6	327.1	327.6
165°	298.5	302.9	306.2	310.0	311.4	312.8	315.0	317.2	316.6	316.1	316.6
167.5°	294.1	297.4	300.1	303.4	304.2	305.1	306.2	307.8	307.8	307.3	307.8
170°	289.7	292.4	294.1	296.3	297.1	297.9	299.0	299.6	299.0	299.0	299.0
172.5°	285.9	288.1	289.2	290.3	290.8	291.4	291.9	292.4	291.9	290.8	291.9
175°	283.1	284.2	284.8	285.9	285.9	285.9	285.9	287.0	285.9	284.8	285.9
177.5°	280.9	281.5	282.0	282.0	282.3	282.6	282.0	282.6	281.5	280.4	281.5
180°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9
2.5°	591.1	588.0	587.5	587.5	582.7	585.3	580.0	574.2	571.6	571.6	566.7
5°	640.3	637.2	634.1	629.2	629.2	626.5	618.1	609.7	603.5	598.2	592.4
7.5°	690.8	687.7	678.8	673.9	676.6	671.3	660.2	646.0	635.4	627.0	615.0
10°	745.7	737.3	732.9	730.2	720.9	715.1	702.3	681.5	668.2	657.1	641.6
12.5°	790.5	793.1	776.3	777.6	768.3	760.3	740.4	720.5	700.5	685.0	662.0
15°	838.8	830.8	820.6	812.6	809.5	799.8	782.9	756.3	734.6	710.3	684.1
17.5°	876.9	870.7	860.9	853.4	846.7	823.3	809.1	785.6	755.9	732.0	700.1
20°	909.2	903.4	889.7	884.8	872.9	856.0	835.7	799.3	772.7	746.6	715.6
22.5°	922.9	917.2	905.2	899.0	891.5	875.1	855.6	821.0	788.2	755.5	722.7
25°	911.4	911.4	905.7	903.4	896.8	882.2	862.2	833.0	798.0	762.5	723.6
27.5°	855.6	866.7	870.7	872.9	872.9	873.3	859.6	831.2	797.1	762.5	721.8
30°	775.0	793.6	810.0	814.8	823.3	832.6	838.3	824.6	794.0	757.7	716.9
32.5°	673.5	697.4	728.0	735.5	747.0	775.0	790.5	796.2	779.4	747.5	704.1
35°	572.5	602.6	621.2	644.2	654.9	696.1	730.6	751.5	747.5	728.4	689.0
37.5°	484.3	501.6	524.2	548.5	569.8	609.2	652.2	692.5	708.9	699.6	669.9
40°	399.7	420.0	447.1	467.0	481.6	521.1	574.2	618.1	654.0	659.8	641.6
42.5°	339.8	360.2	376.6	398.3	409.9	448.0	494.9	549.9	592.4	615.0	607.0
45°	293.8	306.2	319.5	331.9	346.0	379.7	423.1	483.4	531.3	563.2	566.3
47.5°	253.4	264.5	276.0	287.6	295.5	321.7	361.6	410.7	463.0	506.9	524.2
50°	225.1	230.4	238.8	245.5	254.8	277.4	309.3	351.8	407.2	454.6	477.2
52.5°	197.2	203.8	210.5	216.2	222.4	238.4	267.6	304.4	352.3	401.0	428.9
55°	173.7	179.0	185.2	189.2	192.7	206.9	229.1	257.4	298.6	344.7	379.3
57.5°	154.6	156.9	162.2	164.4	168.4	179.9	195.8	221.1	254.3	299.1	327.4
60°	133.8	138.2	142.2	144.0	147.1	155.1	166.2	189.6	218.4	251.2	283.6
62.5°	117.0	118.7	121.8	124.1	126.3	134.7	144.0	161.7	183.4	210.9	240.6
65°	101.5	102.4	104.1	107.2	108.6	114.8	120.1	132.9	153.3	174.1	203.8
67.5°	85.5	86.4	88.6	90.4	91.7	95.7	101.5	110.8	121.8	144.9	161.3
70°	73.1	73.1	74.4	75.3	76.7	78.4	81.5	88.6	98.8	113.4	128.5
72.5°	61.1	61.1	61.1	62.5	62.5	63.8	65.6	70.5	77.5	89.1	98.8
75°	47.4	47.9	48.7	48.7	49.2	51.0	52.3	53.6	57.2	64.7	73.6
77.5°	35.9	36.8	37.2	36.3	37.2	37.2	39.0	40.8	42.5	44.8	51.4
80°	26.6	27.0	26.1	26.6	26.6	27.5	28.4	27.9	28.8	31.5	33.2
82.5°	17.7	18.2	18.2	18.2	18.2	19.5	19.5	19.1	19.5	19.9	20.4
85°	11.1	10.6	10.6	11.1	10.6	10.6	11.1	11.5	11.1	11.5	12.0
87.5°	4.9	4.9	4.9	4.9	4.4	4.4	4.9	4.4	4.9	4.4	4.0
90°	12.1	11.5	11.0	11.0	11.0	10.4	9.9	9.3	9.9	8.8	7.7
92.5°	52.2	56.1	64.3	71.2	78.1	98.9	132.5	179.2	215.5	188.6	136.9
95°	151.2	168.2	195.1	221.8	248.5	322.1	407.3	460.7	448.0	338.1	206.7
97.5°	351.8	384.8	422.2	453.0	483.8	544.2	586.5	577.8	479.4	323.8	188.6
100°	525.0	558.5	606.3	626.6	647.0	674.0	663.0	582.7	442.0	287.0	174.8
102.5°	683.3	705.3	730.0	735.5	741.0	724.5	659.1	541.5	395.2	262.2	171.0
105°	784.4	788.8	787.7	776.4	765.2	710.8	615.7	489.8	360.6	250.1	173.2
107.5°	821.3	811.4	787.2	764.1	741.0	665.2	562.4	447.5	338.1	246.8	179.8
110°	812.5	789.4	750.4	720.2	689.9	610.2	515.1	417.2	327.6	247.9	187.5

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	771.3	742.1	696.5	666.2	636.0	561.8	480.5	400.2	322.7	251.2	195.7
115°	720.7	687.7	644.3	617.9	591.5	527.2	459.6	390.8	321.6	255.6	204.5
117.5°	670.1	641.5	603.0	580.0	556.9	504.6	447.5	385.9	321.0	260.0	213.3
120°	629.4	605.2	573.9	554.4	534.9	490.9	439.8	382.1	321.0	265.0	222.6
122.5°	599.2	579.4	554.1	537.6	521.1	482.1	433.2	377.7	320.5	269.9	231.4
125°	578.9	562.9	540.9	525.8	510.7	472.8	425.5	372.7	319.9	274.9	240.2
127.5°	565.1	550.8	528.8	514.5	500.2	462.3	416.7	366.1	318.8	278.7	247.9
130°	551.9	538.2	515.6	501.0	486.5	449.1	405.7	360.1	318.3	283.1	255.1
132.5°	537.6	521.7	499.7	485.2	470.6	434.3	394.1	354.6	317.7	287.0	262.2
135°	517.8	502.4	480.5	466.8	453.0	419.4	383.7	349.1	317.2	290.8	268.3
137.5°	496.4	480.5	459.6	447.0	434.3	405.1	373.8	344.1	317.2	293.0	272.7
140°	470.6	458.5	439.2	427.6	416.1	391.4	365.6	340.3	316.6	295.7	277.1
142.5°	446.9	435.9	419.4	409.8	400.2	379.9	357.9	337.0	316.6	297.9	280.4
145°	424.4	415.0	401.3	393.6	385.9	369.4	350.7	333.1	315.5	298.5	282.6
147.5°	405.1	396.9	386.5	380.2	373.8	360.1	344.7	329.8	313.9	299.0	284.8
150°	388.7	381.5	372.7	367.8	362.8	351.8	339.2	326.0	312.2	299.0	286.4
152.5°	373.8	368.3	361.2	357.4	353.5	343.6	333.1	321.6	309.5	297.9	287.5
155°	360.6	356.2	350.7	347.4	344.1	335.9	327.1	317.2	306.7	296.8	288.1
157.5°	348.5	345.2	340.8	338.0	335.3	328.2	320.5	312.8	304.0	295.7	288.1
160°	337.5	334.2	330.9	328.7	326.5	320.5	314.4	307.8	300.7	294.1	288.1
162.5°	327.1	323.8	321.6	319.6	317.7	313.3	308.4	303.4	297.4	292.4	288.1
165°	317.2	315.0	312.8	311.4	310.0	306.2	302.9	298.5	294.1	290.3	287.0
167.5°	307.8	306.2	305.1	304.2	303.4	300.1	297.4	294.1	290.8	288.1	285.9
170°	299.6	299.0	297.9	297.1	296.3	294.1	292.4	289.7	287.5	285.9	284.8
172.5°	292.4	291.9	291.4	290.8	290.3	289.2	288.1	285.9	284.2	283.7	283.7
175°	287.0	285.9	285.9	285.9	285.9	284.8	284.2	283.1	282.0	282.0	282.6
177.5°	282.6	282.0	282.6	282.3	282.0	282.0	281.5	280.9	280.4	280.4	281.5
180°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9
2.5°	564.0	561.8	560.5	560.1	556.1	553.9	552.5	551.6	550.3	546.8	543.7
5°	585.3	579.1	576.0	572.5	566.3	559.2	553.4	549.9	545.4	538.3	531.7
7.5°	605.3	595.9	589.7	584.9	574.2	562.7	553.4	545.9	537.5	527.7	518.4
10°	626.1	611.0	603.0	595.5	580.0	564.9	551.6	540.6	528.6	515.7	505.6
12.5°	642.5	622.5	613.7	603.0	584.0	566.3	549.4	534.4	518.9	505.1	490.5
15°	661.5	636.7	626.5	612.8	586.6	563.6	541.9	525.5	509.5	489.2	473.7
17.5°	672.6	643.8	629.2	617.2	588.9	560.9	535.7	515.3	496.7	476.3	459.9
20°	683.7	650.9	634.5	617.7	584.0	554.3	527.7	503.3	483.8	461.7	444.9
22.5°	687.2	649.1	631.8	616.3	580.9	547.7	517.1	492.3	469.7	447.5	428.5
25°	687.2	648.7	628.3	608.4	571.1	537.0	506.4	479.4	454.2	432.0	413.0
27.5°	680.1	639.8	618.5	600.4	561.8	525.1	493.6	463.9	439.5	417.4	395.7
30°	671.3	627.0	605.7	584.0	546.8	511.8	477.6	450.2	424.5	399.2	379.7
32.5°	660.2	613.2	589.7	567.6	528.2	491.8	460.4	433.3	409.0	382.8	361.1
35°	644.2	592.8	566.7	547.2	509.1	471.4	441.3	414.7	391.2	364.2	340.7
37.5°	623.9	574.2	547.7	523.7	484.3	449.7	421.4	395.7	372.6	347.8	321.7
40°	599.9	548.1	525.1	499.8	458.1	425.4	398.8	375.7	352.7	329.2	304.0
42.5°	572.9	521.5	495.8	471.4	431.6	399.2	374.4	353.6	332.3	310.6	283.6
45°	540.6	492.3	467.5	444.4	405.9	372.6	350.0	330.1	311.9	289.8	265.9
47.5°	504.2	462.1	436.9	412.1	374.4	345.6	323.5	306.6	291.1	269.0	247.2
50°	468.8	427.1	406.8	381.5	346.9	319.9	297.3	283.1	271.2	249.5	230.0
52.5°	424.0	392.6	373.1	351.4	318.1	290.7	272.9	260.5	246.4	229.5	212.2
55°	384.6	355.4	339.8	319.5	286.7	262.3	247.2	235.7	224.6	209.6	195.8
57.5°	339.8	321.7	306.2	288.4	256.1	235.3	222.0	212.2	202.0	189.6	178.6
60°	292.9	284.5	269.4	255.2	227.7	209.6	198.5	189.6	179.9	169.7	160.4
62.5°	251.2	246.4	237.5	226.4	200.7	185.2	174.1	167.5	160.4	151.1	142.2
65°	211.8	209.6	201.2	193.2	175.5	161.7	152.0	148.0	140.0	132.9	124.9
67.5°	176.8	174.1	169.3	165.7	150.6	137.8	132.9	127.6	121.0	115.6	109.0
70°	141.3	140.9	137.8	133.4	125.4	116.1	111.2	107.7	101.0	97.0	92.2
72.5°	109.9	112.1	109.4	107.7	102.4	95.7	91.3	89.1	83.7	80.6	77.1
75°	82.0	83.7	85.1	82.0	80.6	77.5	73.6	71.3	68.7	64.2	62.9
77.5°	55.8	59.8	59.8	60.7	61.1	59.4	56.3	54.5	51.4	50.5	48.7
80°	36.8	40.3	40.8	41.6	43.0	43.0	40.8	40.3	37.2	36.8	35.4
82.5°	21.3	24.4	26.1	27.5	27.0	28.8	27.0	26.6	24.8	24.8	23.9
85°	11.5	12.0	12.8	13.7	14.6	15.5	15.5	15.1	14.6	14.2	13.3
87.5°	4.4	4.4	4.9	4.4	4.9	5.8	6.2	6.2	5.8	5.3	4.4
90°	7.7	4.4	4.4	4.4	3.8	3.3	1.6	0.5	1.6	3.3	3.8
92.5°	83.6	49.5	42.4	35.2	25.3	17.0	11.0	7.7	11.0	17.0	25.3
95°	116.5	68.7	57.2	45.6	32.4	25.3	19.8	18.1	19.8	25.3	32.4
97.5°	111.0	73.1	63.2	53.3	41.8	35.2	30.2	30.2	30.2	35.2	41.8
100°	112.7	80.3	71.5	62.7	52.2	45.6	41.8	41.8	41.8	45.6	52.2
102.5°	118.2	89.6	81.4	73.1	63.2	57.2	53.9	52.8	53.9	57.2	63.2
105°	127.5	101.1	93.2	85.2	75.3	68.7	66.0	64.3	66.0	68.7	75.3
107.5°	137.4	113.2	105.2	97.3	88.0	80.8	78.1	77.0	78.1	80.8	88.0
110°	149.0	124.8	117.4	109.9	100.0	93.5	90.7	89.6	90.7	93.5	100.0

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	160.0	136.9	129.4	122.0	112.1	106.1	102.8	101.7	102.8	106.1	112.1
115°	171.5	149.5	142.1	134.7	124.2	118.7	114.9	113.2	114.9	118.7	124.2
117.5°	182.5	161.6	153.9	146.2	136.3	130.3	127.0	125.3	127.0	130.3	136.3
120°	194.1	173.2	165.5	157.8	148.4	142.4	138.5	137.4	138.5	142.4	148.4
122.5°	205.0	184.2	176.8	169.3	158.9	153.4	149.5	148.4	149.5	153.4	158.9
125°	214.9	195.1	187.4	179.8	169.3	163.3	160.0	157.8	160.0	163.3	169.3
127.5°	224.3	205.0	197.4	189.7	178.7	172.1	168.2	166.6	168.2	172.1	178.7
130°	233.6	214.9	207.0	199.0	188.6	180.3	175.9	173.7	175.9	180.3	188.6
132.5°	241.3	222.6	215.2	207.8	196.2	188.6	182.5	180.9	182.5	188.6	196.2
135°	248.5	230.3	223.2	216.0	204.5	195.1	189.7	187.5	189.7	195.1	204.5
137.5°	254.0	236.9	230.0	223.2	211.1	202.3	196.2	194.1	196.2	202.3	211.1
140°	259.5	243.0	236.4	229.8	218.2	208.9	202.8	201.2	202.8	208.9	218.2
142.5°	264.4	248.5	242.2	235.8	224.8	216.0	210.5	208.9	210.5	216.0	224.8
145°	267.7	253.4	247.4	241.3	230.9	223.2	217.7	216.0	217.7	223.2	230.9
147.5°	271.6	257.8	252.3	246.8	238.0	229.8	224.8	224.3	224.8	229.8	238.0
150°	274.3	262.2	257.0	251.8	243.5	236.9	232.5	232.0	232.5	236.9	243.5
152.5°	276.5	266.1	261.4	256.7	249.6	243.5	239.1	239.1	239.1	243.5	249.6
155°	278.7	269.4	265.2	261.1	255.1	249.6	246.3	245.7	246.3	249.6	255.1
157.5°	280.4	272.1	268.8	265.5	260.0	255.6	252.3	252.3	252.3	255.6	260.0
160°	281.5	274.9	271.8	268.8	264.4	260.6	258.4	258.4	258.4	260.6	264.4
162.5°	282.6	276.5	274.3	272.1	268.3	265.0	263.3	263.9	263.3	265.0	268.3
165°	282.6	277.6	276.0	274.3	271.6	268.8	267.7	267.7	267.7	268.8	271.6
167.5°	282.6	278.7	277.4	276.0	274.3	272.1	271.6	272.1	271.6	272.1	274.3
170°	282.0	279.3	278.5	277.6	276.5	274.9	274.3	274.9	274.3	274.9	276.5
172.5°	281.5	279.8	279.2	278.7	278.2	277.1	277.1	277.6	277.1	277.1	278.2
175°	280.9	279.8	279.8	279.8	279.3	278.7	278.7	279.3	278.7	278.7	279.3
177.5°	280.4	279.8	279.8	279.8	279.8	279.3	279.8	280.4	279.8	279.3	279.8
180°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9
2.5°	541.0	540.1	539.2	535.7	532.6	527.3	522.8	521.1	520.6	521.1	519.7
5°	525.5	525.1	522.0	515.7	510.0	503.8	499.4	494.9	492.3	492.3	489.2
7.5°	510.9	507.8	505.1	497.1	490.5	482.1	475.4	471.4	469.2	464.4	464.4
10°	495.4	490.9	487.4	479.9	470.1	461.7	453.3	448.4	444.4	440.9	439.5
12.5°	479.9	476.3	469.7	461.7	451.9	441.3	432.5	428.9	419.6	412.1	412.5
15°	465.2	457.3	454.2	442.6	431.1	420.9	408.1	397.9	390.4	385.5	379.3
17.5°	448.8	440.9	435.1	425.4	410.3	394.3	381.9	368.2	360.7	352.3	348.3
20°	430.7	424.0	419.6	404.1	385.9	366.9	353.1	344.7	336.3	330.1	326.6
22.5°	415.2	406.8	401.4	380.6	360.7	341.6	331.0	323.9	316.8	311.5	309.7
25°	395.2	390.4	377.5	359.3	335.0	322.1	312.8	303.5	299.5	296.0	292.0
27.5°	378.8	366.9	358.0	334.1	319.0	304.4	295.1	288.0	283.1	279.6	276.5
30°	358.5	347.4	335.0	315.0	301.3	287.6	279.1	273.4	268.1	265.9	263.2
32.5°	337.2	327.0	315.0	299.1	282.2	271.6	265.0	258.8	255.2	253.0	249.9
35°	318.1	305.3	297.3	282.2	268.5	256.5	250.3	245.0	241.0	240.2	239.7
37.5°	297.8	288.0	280.5	265.0	253.4	243.3	237.5	231.7	229.5	229.1	227.3
40°	280.0	271.6	264.5	249.9	237.5	228.2	223.8	220.2	218.0	218.0	217.6
42.5°	264.5	255.7	248.6	235.3	224.2	215.8	210.9	207.4	206.5	206.9	206.5
45°	247.2	239.7	232.6	218.9	209.6	203.4	198.1	196.3	195.0	195.4	195.8
47.5°	230.8	224.6	217.6	206.5	195.8	189.2	186.1	184.3	184.3	184.3	185.2
50°	216.2	209.1	202.9	191.4	181.7	176.3	173.7	171.5	171.9	172.4	172.8
52.5°	198.9	192.7	188.3	176.8	169.7	163.1	160.0	160.4	160.0	160.0	160.8
55°	183.9	177.7	173.2	162.6	155.5	151.1	148.4	147.1	147.5	146.7	148.4
57.5°	167.0	161.7	158.6	148.4	142.2	138.2	136.0	133.8	134.7	134.3	133.8
60°	152.4	146.2	141.3	134.3	128.9	124.1	122.7	120.5	121.4	120.5	120.1
62.5°	135.6	130.7	127.2	120.1	115.6	111.7	108.6	107.2	106.8	105.5	104.1
65°	118.7	116.1	112.5	105.5	101.0	97.9	96.1	94.8	94.4	90.8	86.8
67.5°	103.2	101.5	97.9	92.6	88.6	85.5	82.9	80.6	78.0	75.3	73.1
70°	88.6	86.0	83.7	78.9	75.3	72.2	69.6	66.9	65.6	62.9	62.0
72.5°	74.4	71.8	69.6	65.1	62.0	58.9	58.0	54.9	53.6	53.2	53.2
75°	59.8	57.6	56.3	52.3	49.6	47.4	46.1	45.2	44.3	43.4	42.1
77.5°	45.6	44.3	43.4	40.8	38.5	37.2	36.8	33.7	32.8	31.9	31.0
80°	33.2	32.8	31.9	29.7	28.8	25.7	25.7	24.8	24.4	24.4	24.4
82.5°	22.6	21.7	21.3	19.1	18.6	18.2	17.7	17.3	17.7	17.3	17.7
85°	12.0	11.5	11.1	11.1	11.1	11.1	11.1	11.1	11.1	10.6	11.1
87.5°	4.4	4.4	4.4	4.4	4.0	4.4	4.4	4.0	4.4	4.4	4.4
90°	4.4	4.4	4.4	7.7	7.7	8.8	9.9	9.3	9.9	10.4	11.0
92.5°	35.2	42.4	49.5	83.6	136.9	188.6	215.5	179.2	132.5	98.9	78.1
95°	45.6	57.2	68.7	116.5	206.7	338.1	448.0	460.7	407.3	322.1	248.5
97.5°	53.3	63.2	73.1	111.0	188.6	323.8	479.4	577.8	586.5	544.2	483.8
100°	62.7	71.5	80.3	112.7	174.8	287.0	442.0	582.7	663.0	674.0	647.0
102.5°	73.1	81.4	89.6	118.2	171.0	262.2	395.2	541.5	659.1	724.5	741.0
105°	85.2	93.2	101.1	127.5	173.2	250.1	360.6	489.8	615.7	710.8	765.2
107.5°	97.3	105.2	113.2	137.4	179.8	246.8	338.1	447.5	562.4	665.2	741.0
110°	109.9	117.4	124.8	149.0	187.5	247.9	327.6	417.2	515.1	610.2	689.9

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	122.0	129.4	136.9	160.0	195.7	251.2	322.7	400.2	480.5	561.8	636.0
115°	134.7	142.1	149.5	171.5	204.5	255.6	321.6	390.8	459.6	527.2	591.5
117.5°	146.2	153.9	161.6	182.5	213.3	260.0	321.0	385.9	447.5	504.6	556.9
120°	157.8	165.5	173.2	194.1	222.6	265.0	321.0	382.1	439.8	490.9	534.9
122.5°	169.3	176.8	184.2	205.0	231.4	269.9	320.5	377.7	433.2	482.1	521.1
125°	179.8	187.4	195.1	214.9	240.2	274.9	319.9	372.7	425.5	472.8	510.7
127.5°	189.7	197.4	205.0	224.3	247.9	278.7	318.8	366.1	416.7	462.3	500.2
130°	199.0	207.0	214.9	233.6	255.1	283.1	318.3	360.1	405.7	449.1	486.5
132.5°	207.8	215.2	222.6	241.3	262.2	287.0	317.7	354.6	394.1	434.3	470.6
135°	216.0	223.2	230.3	248.5	268.3	290.8	317.2	349.1	383.7	419.4	453.0
137.5°	223.2	230.0	236.9	254.0	272.7	293.0	317.2	344.1	373.8	405.1	434.3
140°	229.8	236.4	243.0	259.5	277.1	295.7	316.6	340.3	365.6	391.4	416.1
142.5°	235.8	242.2	248.5	264.4	280.4	297.9	316.6	337.0	357.9	379.9	400.2
145°	241.3	247.4	253.4	267.7	282.6	298.5	315.5	333.1	350.7	369.4	385.9
147.5°	246.8	252.3	257.8	271.6	284.8	299.0	313.9	329.8	344.7	360.1	373.8
150°	251.8	257.0	262.2	274.3	286.4	299.0	312.2	326.0	339.2	351.8	362.8
152.5°	256.7	261.4	266.1	276.5	287.5	297.9	309.5	321.6	333.1	343.6	353.5
155°	261.1	265.2	269.4	278.7	288.1	296.8	306.7	317.2	327.1	335.9	344.1
157.5°	265.5	268.8	272.1	280.4	288.1	295.7	304.0	312.8	320.5	328.2	335.3
160°	268.8	271.8	274.9	281.5	288.1	294.1	300.7	307.8	314.4	320.5	326.5
162.5°	272.1	274.3	276.5	282.6	288.1	292.4	297.4	303.4	308.4	313.3	317.7
165°	274.3	276.0	277.6	282.6	287.0	290.3	294.1	298.5	302.9	306.2	310.0
167.5°	276.0	277.4	278.7	282.6	285.9	288.1	290.8	294.1	297.4	300.1	303.4
170°	277.6	278.5	279.3	282.0	284.8	285.9	287.5	289.7	292.4	294.1	296.3
172.5°	278.7	279.2	279.8	281.5	283.7	283.7	284.2	285.9	288.1	289.2	290.3
175°	279.8	279.8	279.8	280.9	282.6	282.0	282.0	283.1	284.2	284.8	285.9
177.5°	279.8	279.8	279.8	280.4	281.5	280.4	280.4	280.9	281.5	282.0	282.0
180°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9
2.5°	519.7	521.5	519.3	520.6	517.5	517.1	517.5	517.5	518.0	518.4	518.9
5°	490.5	490.1	487.4	485.6	484.3	485.6	486.5	487.4	486.5	487.4	487.8
7.5°	463.0	461.7	460.4	457.3	458.1	457.3	459.9	458.6	458.6	460.8	462.6
10°	438.7	436.0	435.1	431.6	428.9	428.5	431.6	432.9	434.2	435.1	438.7
12.5°	407.2	403.2	400.1	401.4	393.9	397.0	397.9	396.1	401.4	407.6	404.1
15°	373.5	374.0	367.8	365.5	359.3	361.1	361.6	366.0	370.4	370.0	375.3
17.5°	348.7	346.0	340.7	340.3	337.6	339.0	338.5	342.1	340.7	342.9	347.4
20°	325.7	323.9	319.5	317.7	318.6	317.7	318.1	318.6	319.9	324.8	323.9
22.5°	307.5	305.3	305.3	303.1	300.4	299.5	301.7	303.1	304.8	305.7	307.9
25°	291.5	289.8	287.6	286.2	284.0	284.5	285.8	287.6	288.9	290.7	292.4
27.5°	275.2	275.2	272.9	272.5	271.6	271.2	272.9	273.8	273.8	275.2	276.9
30°	262.3	262.3	260.1	259.6	259.2	259.2	260.5	261.0	261.4	262.7	263.6
32.5°	249.9	249.5	248.6	249.0	248.6	249.0	249.0	249.5	250.3	250.8	252.6
35°	238.4	238.8	237.9	237.9	237.5	237.9	238.8	239.3	239.7	240.6	240.6
37.5°	227.3	228.2	227.7	229.1	229.1	229.1	229.1	230.0	230.0	230.0	229.5
40°	217.6	217.6	217.1	218.0	218.9	218.9	219.3	219.3	219.8	219.8	219.3
42.5°	206.5	207.4	208.7	209.1	210.0	209.6	210.9	210.5	210.9	210.0	209.1
45°	196.3	196.3	198.1	199.8	200.3	200.3	200.3	201.2	200.3	198.9	198.5
47.5°	185.2	186.1	187.0	189.2	189.6	189.6	189.6	189.6	188.8	188.8	188.8
50°	174.1	174.6	175.0	175.9	177.2	176.8	176.8	176.8	178.6	176.8	177.2
52.5°	160.8	161.3	161.7	163.5	163.1	163.1	163.5	163.5	164.8	164.4	163.5
55°	147.5	147.5	148.4	148.4	148.4	149.3	149.8	150.6	150.2	150.6	151.1
57.5°	134.3	133.4	132.9	132.9	134.3	133.8	134.3	134.3	136.0	136.9	137.4
60°	118.7	118.7	118.3	115.6	115.6	115.2	116.5	117.4	118.3	122.3	121.8
62.5°	102.8	101.0	99.3	99.7	97.0	98.4	97.5	98.4	101.0	104.1	104.6
65°	86.8	85.5	83.7	83.3	82.4	83.7	83.3	83.7	85.1	86.8	89.1
67.5°	72.7	72.2	71.3	70.9	70.9	70.9	71.8	71.8	72.2	73.6	74.9
70°	62.0	61.6	62.0	61.1	61.6	61.1	61.6	62.0	62.5	62.9	64.2
72.5°	52.3	52.3	52.3	51.4	52.3	51.8	51.8	52.3	52.7	53.2	54.1
75°	41.6	40.8	39.9	39.0	38.5	39.4	39.9	39.4	40.8	42.5	42.5
77.5°	31.5	31.0	31.0	31.0	31.5	31.0	31.9	31.5	31.9	31.9	32.8
80°	24.4	23.9	24.4	24.4	23.9	24.8	24.4	24.4	24.8	25.3	24.8
82.5°	17.7	18.2	17.7	17.7	17.7	18.6	17.7	17.7	17.7	18.2	18.2
85°	11.1	11.1	11.1	11.1	11.5	11.1	11.5	11.1	12.0	11.5	11.5
87.5°	4.0	4.4	4.9	4.9	4.9	4.9	4.4	4.9	5.3	4.9	5.3
90°	11.0	11.0	11.5	12.1	11.5	11.5	11.5	12.1	11.5	11.0	11.0
92.5°	71.2	64.3	56.1	52.2	50.0	50.0	50.0	52.2	56.1	64.3	71.2
95°	221.8	195.1	168.2	151.2	141.3	134.1	141.3	151.2	168.2	195.1	221.8
97.5°	453.0	422.2	384.8	351.8	335.3	322.1	335.3	351.8	384.8	422.2	453.0
100°	626.6	606.3	558.5	525.0	508.5	504.1	508.5	525.0	558.5	606.3	626.6
102.5°	735.5	730.0	705.3	683.3	665.7	662.4	665.7	683.3	705.3	730.0	735.5
105°	776.4	787.7	788.8	784.4	776.8	773.5	776.8	784.4	788.8	787.7	776.4
107.5°	764.1	787.2	811.4	821.3	825.7	826.2	825.7	821.3	811.4	787.2	764.1
110°	720.2	750.4	789.4	812.5	822.4	827.3	822.4	812.5	789.4	750.4	720.2

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	666.2	696.5	742.1	771.3	786.1	794.9	786.1	771.3	742.1	696.5	666.2
115°	617.9	644.3	687.7	720.7	738.3	742.7	738.3	720.7	687.7	644.3	617.9
117.5°	580.0	603.0	641.5	670.1	688.8	691.5	688.8	670.1	641.5	603.0	580.0
120°	554.4	573.9	605.2	629.4	643.7	649.8	643.7	629.4	605.2	573.9	554.4
122.5°	537.6	554.1	579.4	599.2	610.7	616.8	610.7	599.2	579.4	554.1	537.6
125°	525.8	540.9	562.9	578.9	589.3	592.6	589.3	578.9	562.9	540.9	525.8
127.5°	514.5	528.8	550.8	565.1	573.9	577.2	573.9	565.1	550.8	528.8	514.5
130°	501.0	515.6	538.2	551.9	560.7	564.0	560.7	551.9	538.2	515.6	501.0
132.5°	485.2	499.7	521.7	537.6	545.9	549.2	545.9	537.6	521.7	499.7	485.2
135°	466.8	480.5	502.4	517.8	526.6	529.9	526.6	517.8	502.4	480.5	466.8
137.5°	447.0	459.6	480.5	496.4	503.5	507.4	503.5	496.4	480.5	459.6	447.0
140°	427.6	439.2	458.5	470.6	478.3	482.7	478.3	470.6	458.5	439.2	427.6
142.5°	409.8	419.4	435.9	446.9	453.5	456.3	453.5	446.9	435.9	419.4	409.8
145°	393.6	401.3	415.0	424.4	429.9	432.6	429.9	424.4	415.0	401.3	393.6
147.5°	380.2	386.5	396.9	405.1	409.5	410.6	409.5	405.1	396.9	386.5	380.2
150°	367.8	372.7	381.5	388.7	391.9	392.5	391.9	388.7	381.5	372.7	367.8
152.5°	357.4	361.2	368.3	373.8	375.5	376.0	375.5	373.8	368.3	361.2	357.4
155°	347.4	350.7	356.2	360.6	362.3	362.3	362.3	360.6	356.2	350.7	347.4
157.5°	338.0	340.8	345.2	348.5	349.6	349.6	349.6	348.5	345.2	340.8	338.0
160°	328.7	330.9	334.2	337.5	338.1	338.1	338.1	337.5	334.2	330.9	328.7
162.5°	319.6	321.6	323.8	327.1	327.6	327.1	327.6	327.1	323.8	321.6	319.6
165°	311.4	312.8	315.0	317.2	316.6	316.1	316.6	317.2	315.0	312.8	311.4
167.5°	304.2	305.1	306.2	307.8	307.8	307.3	307.8	307.8	306.2	305.1	304.2
170°	297.1	297.9	299.0	299.6	299.0	299.0	299.0	299.6	299.0	297.9	297.1
172.5°	290.8	291.4	291.9	292.4	291.9	290.8	291.9	292.4	291.9	291.4	290.8
175°	285.9	285.9	285.9	287.0	285.9	284.8	285.9	287.0	285.9	285.9	285.9
177.5°	282.3	282.6	282.0	282.6	281.5	280.4	281.5	282.6	282.0	282.6	282.3
180°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9	549.9
2.5°	520.6	522.8	522.0	518.9	520.2	522.8	525.5	529.0	531.3	533.0	533.9
5°	490.1	494.0	493.2	493.2	494.9	499.4	503.8	511.3	514.0	517.1	521.5
7.5°	463.0	466.1	468.8	469.7	472.3	478.1	483.8	492.3	498.9	502.5	505.1
10°	439.1	441.3	445.3	447.5	450.2	457.3	465.7	474.5	481.2	487.4	490.9
12.5°	408.5	417.4	422.7	426.2	429.8	440.4	447.1	456.8	464.8	470.6	475.9
15°	374.4	385.0	388.1	401.9	410.7	419.2	429.3	440.9	448.4	455.0	462.1
17.5°	345.6	353.1	356.7	371.3	378.8	392.1	406.8	421.4	432.9	437.8	444.9
20°	327.4	331.4	338.5	343.4	351.4	366.9	382.8	400.5	417.8	422.7	429.8
22.5°	308.8	314.1	319.0	325.7	331.9	342.5	358.5	378.0	396.6	405.4	413.8
25°	292.0	297.3	300.4	307.5	313.3	323.9	335.0	354.9	377.1	384.6	397.9
27.5°	278.7	281.8	287.1	290.2	296.9	306.6	316.8	331.9	353.6	366.4	379.3
30°	265.4	267.6	272.1	276.5	281.4	288.0	299.5	314.1	334.1	345.2	358.0
32.5°	252.1	255.7	258.3	261.4	266.7	274.7	282.7	296.9	312.8	325.2	338.1
35°	241.0	242.4	245.9	249.5	253.0	260.1	268.5	282.2	296.4	306.2	317.7
37.5°	229.1	231.3	233.9	235.3	241.0	245.5	254.3	265.0	281.8	288.0	299.5
40°	219.8	219.3	222.0	224.2	226.9	233.9	239.3	250.8	264.1	273.8	280.9
42.5°	208.2	208.2	209.1	211.8	215.3	219.8	226.0	235.7	249.5	256.5	265.0
45°	198.9	197.6	198.1	199.8	202.0	206.5	212.7	221.1	234.8	240.6	249.5
47.5°	187.9	186.5	186.5	188.3	190.1	193.2	198.1	207.8	218.9	226.4	233.1
50°	175.5	175.9	175.5	176.8	177.7	180.8	186.1	194.1	204.3	210.5	218.0
52.5°	163.9	163.1	162.6	163.5	165.3	167.5	173.2	180.3	190.1	196.3	202.9
55°	149.8	150.6	150.6	150.6	153.3	154.2	158.6	165.7	175.5	180.3	186.5
57.5°	136.9	136.5	137.4	136.9	139.1	142.2	145.8	151.1	160.8	165.7	171.5
60°	122.7	123.2	123.6	123.6	125.4	128.5	132.5	137.4	145.3	150.2	155.5
62.5°	105.5	107.7	109.9	110.8	113.4	115.6	118.3	123.6	130.7	134.3	139.1
65°	89.1	92.2	95.3	97.5	99.3	101.5	105.0	109.9	115.6	119.2	124.1
67.5°	74.9	77.1	81.1	83.3	86.8	89.5	91.7	95.7	102.8	104.1	108.1
70°	64.7	65.6	67.3	69.1	73.1	75.3	78.0	82.0	87.3	90.4	92.6
72.5°	54.5	54.9	55.8	57.6	59.4	62.0	65.1	68.7	73.6	74.9	78.0
75°	43.4	46.1	46.1	47.4	48.7	50.1	52.7	56.3	59.4	61.6	63.4
77.5°	32.3	33.7	34.6	36.8	38.5	39.9	41.6	44.3	46.1	47.9	49.2
80°	25.3	25.7	26.1	26.1	27.0	28.8	30.6	32.3	34.6	35.4	36.8
82.5°	18.6	18.6	18.6	19.5	19.9	20.4	20.4	21.3	23.5	24.4	25.7
85°	12.0	12.0	12.0	12.0	12.4	12.8	13.3	13.7	13.7	13.7	14.6
87.5°	4.9	5.8	5.3	5.8	5.8	5.8	5.8	6.2	6.2	6.6	6.6
90°	11.0	10.4	9.9	9.3	9.9	8.8	7.7	7.7	4.4	4.4	4.4
92.5°	78.1	98.9	132.5	179.2	215.5	188.6	136.9	83.6	49.5	42.4	35.2
95°	248.5	322.1	407.3	460.7	448.0	338.1	206.7	116.5	68.7	57.2	45.6
97.5°	483.8	544.2	586.5	577.8	479.4	323.8	188.6	111.0	73.1	63.2	53.3
100°	647.0	674.0	663.0	582.7	442.0	287.0	174.8	112.7	80.3	71.5	62.7
102.5°	741.0	724.5	659.1	541.5	395.2	262.2	171.0	118.2	89.6	81.4	73.1
105°	765.2	710.8	615.7	489.8	360.6	250.1	173.2	127.5	101.1	93.2	85.2
107.5°	741.0	665.2	562.4	447.5	338.1	246.8	179.8	137.4	113.2	105.2	97.3
110°	689.9	610.2	515.1	417.2	327.6	247.9	187.5	149.0	124.8	117.4	109.9

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	636.0	561.8	480.5	400.2	322.7	251.2	195.7	160.0	136.9	129.4	122.0
115°	591.5	527.2	459.6	390.8	321.6	255.6	204.5	171.5	149.5	142.1	134.7
117.5°	556.9	504.6	447.5	385.9	321.0	260.0	213.3	182.5	161.6	153.9	146.2
120°	534.9	490.9	439.8	382.1	321.0	265.0	222.6	194.1	173.2	165.5	157.8
122.5°	521.1	482.1	433.2	377.7	320.5	269.9	231.4	205.0	184.2	176.8	169.3
125°	510.7	472.8	425.5	372.7	319.9	274.9	240.2	214.9	195.1	187.4	179.8
127.5°	500.2	462.3	416.7	366.1	318.8	278.7	247.9	224.3	205.0	197.4	189.7
130°	486.5	449.1	405.7	360.1	318.3	283.1	255.1	233.6	214.9	207.0	199.0
132.5°	470.6	434.3	394.1	354.6	317.7	287.0	262.2	241.3	222.6	215.2	207.8
135°	453.0	419.4	383.7	349.1	317.2	290.8	268.3	248.5	230.3	223.2	216.0
137.5°	434.3	405.1	373.8	344.1	317.2	293.0	272.7	254.0	236.9	230.0	223.2
140°	416.1	391.4	365.6	340.3	316.6	295.7	277.1	259.5	243.0	236.4	229.8
142.5°	400.2	379.9	357.9	337.0	316.6	297.9	280.4	264.4	248.5	242.2	235.8
145°	385.9	369.4	350.7	333.1	315.5	298.5	282.6	267.7	253.4	247.4	241.3
147.5°	373.8	360.1	344.7	329.8	313.9	299.0	284.8	271.6	257.8	252.3	246.8
150°	362.8	351.8	339.2	326.0	312.2	299.0	286.4	274.3	262.2	257.0	251.8
152.5°	353.5	343.6	333.1	321.6	309.5	297.9	287.5	276.5	266.1	261.4	256.7
155°	344.1	335.9	327.1	317.2	306.7	296.8	288.1	278.7	269.4	265.2	261.1
157.5°	335.3	328.2	320.5	312.8	304.0	295.7	288.1	280.4	272.1	268.8	265.5
160°	326.5	320.5	314.4	307.8	300.7	294.1	288.1	281.5	274.9	271.8	268.8
162.5°	317.7	313.3	308.4	303.4	297.4	292.4	288.1	282.6	276.5	274.3	272.1
165°	310.0	306.2	302.9	298.5	294.1	290.3	287.0	282.6	277.6	276.0	274.3
167.5°	303.4	300.1	297.4	294.1	290.8	288.1	285.9	282.6	278.7	277.4	276.0
170°	296.3	294.1	292.4	289.7	287.5	285.9	284.8	282.0	279.3	278.5	277.6
172.5°	290.3	289.2	288.1	285.9	284.2	283.7	283.7	281.5	279.8	279.2	278.7
175°	285.9	284.8	284.2	283.1	282.0	282.0	282.6	280.9	279.8	279.8	279.8
177.5°	282.0	282.0	281.5	280.9	280.4	280.4	281.5	280.4	279.8	279.8	279.8
180°	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8	279.8

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	549.9	549.9	549.9	549.9
2.5°	537.5	540.1	544.6	550.8
5°	525.1	532.6	539.7	549.0
7.5°	514.0	522.8	532.6	545.9
10°	501.1	512.2	524.6	541.0
12.5°	486.1	501.6	515.7	533.5
15°	475.0	486.5	504.7	525.5
17.5°	459.5	475.0	493.2	516.6
20°	444.9	461.3	481.6	506.0
22.5°	429.3	448.0	468.3	494.5
25°	413.4	433.3	453.7	481.6
27.5°	398.8	416.9	440.0	468.3
30°	381.1	401.9	424.0	453.7
32.5°	363.8	385.5	408.1	437.8
35°	345.2	366.9	391.7	420.0
37.5°	327.0	350.9	373.5	401.0
40°	307.1	331.9	355.4	383.3
42.5°	287.6	313.3	336.7	360.7
45°	269.4	294.7	315.9	338.5
47.5°	252.1	274.7	296.4	316.8
50°	235.3	254.3	274.3	291.1
52.5°	217.6	235.7	251.7	266.7
55°	201.6	215.8	230.0	243.7
57.5°	182.6	196.7	209.1	219.8
60°	166.6	175.5	187.4	198.5
62.5°	148.4	158.6	167.9	175.0
65°	130.7	139.6	146.7	152.9
67.5°	115.6	121.0	126.3	132.9
70°	97.5	101.9	108.1	113.0
72.5°	82.0	85.5	88.6	94.4
75°	66.5	69.6	71.3	76.7
77.5°	51.4	54.5	55.8	58.9
80°	39.4	39.9	41.6	44.3
82.5°	27.0	27.9	28.4	30.6
85°	15.5	17.7	17.3	18.2
87.5°	6.6	7.1	8.0	8.9
90°	3.8	3.3	1.6	0.5
92.5°	25.3	17.0	11.0	7.7
95°	32.4	25.3	19.8	18.1
97.5°	41.8	35.2	30.2	30.2
100°	52.2	45.6	41.8	41.8
102.5°	63.2	57.2	53.9	52.8
105°	75.3	68.7	66.0	64.3
107.5°	88.0	80.8	78.1	77.0
110°	100.0	93.5	90.7	89.6

TEST NUMBER: P1026345

CATALOG NUMBER: S124RDIP-B350D590UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	112.1	106.1	102.8	101.7
115°	124.2	118.7	114.9	113.2
117.5°	136.3	130.3	127.0	125.3
120°	148.4	142.4	138.5	137.4
122.5°	158.9	153.4	149.5	148.4
125°	169.3	163.3	160.0	157.8
127.5°	178.7	172.1	168.2	166.6
130°	188.6	180.3	175.9	173.7
132.5°	196.2	188.6	182.5	180.9
135°	204.5	195.1	189.7	187.5
137.5°	211.1	202.3	196.2	194.1
140°	218.2	208.9	202.8	201.2
142.5°	224.8	216.0	210.5	208.9
145°	230.9	223.2	217.7	216.0
147.5°	238.0	229.8	224.8	224.3
150°	243.5	236.9	232.5	232.0
152.5°	249.6	243.5	239.1	239.1
155°	255.1	249.6	246.3	245.7
157.5°	260.0	255.6	252.3	252.3
160°	264.4	260.6	258.4	258.4
162.5°	268.3	265.0	263.3	263.9
165°	271.6	268.8	267.7	267.7
167.5°	274.3	272.1	271.6	272.1
170°	276.5	274.9	274.3	274.9
172.5°	278.2	277.1	277.1	277.6
175°	279.3	278.7	278.7	279.3
177.5°	279.8	279.3	279.8	280.4
180°	279.8	279.8	279.8	279.8

(END OF REPORT)