

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026387

Luminaire Tested: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026387
REPORT IS A COMBINATION OF REPORTS P999437 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6097.0 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	40
1	96	92	88	85	87	84	81	78	69	66	65	55	53	52	42	41	40	40	40	34
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	37	36	34	34	34	29
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	30	30	25
4	73	63	55	50	67	58	51	46	48	43	39	39	35	32	30	28	26	26	26	22
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23	23	23	19
6	62	50	43	37	56	46	40	35	39	34	30	32	28	25	25	22	20	20	20	17
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	23	20	18	18	18	15
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	16	16	14
9	50	38	30	26	45	35	28	24	29	24	21	24	20	18	19	17	15	15	15	12
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	13	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7842	7842	7842	7842
5°	7842	8861	7855	6773
10°	7800	10214	7794	5890
15°	7708	11496	7708	4932
20°	7611	12465	7570	4342
25°	7491	12517	7457	3922
30°	7365	10644	7308	3633
35°	7187	8031	7096	3417
40°	6989	5820	6851	3249
45°	6661	4423	6495	3100
50°	6272	3575	6100	2882
55°	5850	2960	5660	2591
60°	5427	2503	5185	2155
65°	4895	2040	4739	1713
70°	4408	1654	4201	1391
75°	3864	1192	3596	1020
80°	3187	789	2900	750
85°	2314	407	1914	407

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 9817 cd/sqm

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.1	1.5
10°-20°	281.2	4.6
20°-30°	440.5	7.2
30°-40°	489.1	8.0
40°-50°	433.5	7.1
50°-60°	337.8	5.5
60°-70°	221.0	3.6
70°-80°	108.4	1.8
80°-90°	28.4	0.5
90°-100°	364.6	6.0
100°-110°	761.2	12.5
110°-120°	676.7	11.1
120°-130°	569.6	9.3
130°-140°	475.2	7.8
140°-150°	362.8	6.0
150°-160°	255.1	4.2
160°-170°	150.0	2.5
170°-180°	48.8	0.8
0°-30°	814.8	13.4
0°-40°	1304.0	21.4
0°-60°	2075.2	34.0
0°-90°	2433.0	39.9
90°-120°	1802.5	29.6
90°-150°	3210.1	52.7
90°-180°	3664.0	60.1
0°-180°	6097.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	962	962	962	962	962	
5°	960	1111	962	849	960	91
15°	919	1472	919	632	919	259
25°	842	1588	838	498	842	388
35°	735	978	725	416	735	459
45°	592	500	577	350	592	457
55°	426	298	412	261	426	381
65°	267	174	259	146	267	267
75°	134	81	125	69	134	142
85°	32	19	26	19	32	36
90°	1	21	1	21	1	4
95°	33	241	33	241	33	36
105°	116	1391	116	1391	116	123
115°	204	1335	204	1335	204	202
125°	284	1066	284	1066	284	253
135°	337	953	337	953	337	260
145°	388	778	388	778	388	244
155°	442	651	442	651	442	204
165°	481	568	481	568	481	136
175°	502	512	502	512	502	48
180°	503	503	503	503	503	

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	963.2	971.7	976.4	980.3	988.0	991.1	997.3	998.9	1005.1	1004.3	1002.0
5°	960.1	974.8	985.7	997.3	1011.3	1019.0	1027.5	1039.9	1046.1	1054.7	1060.1
7.5°	954.7	974.8	992.7	1010.5	1033.0	1045.4	1056.2	1075.6	1091.9	1105.8	1121.3
10°	946.2	971.7	998.1	1022.1	1053.1	1067.8	1084.1	1112.8	1135.3	1154.6	1179.4
12.5°	933.0	968.6	998.1	1030.6	1070.2	1090.3	1112.0	1146.1	1172.5	1204.2	1235.2
15°	919.1	958.6	997.3	1039.9	1084.9	1108.1	1129.8	1175.6	1215.8	1252.3	1286.4
17.5°	903.6	947.0	989.6	1036.8	1091.1	1119.8	1145.3	1200.3	1244.5	1291.8	1325.9
20°	885.0	932.2	981.0	1033.7	1095.0	1126.7	1155.4	1218.2	1267.0	1318.1	1360.8
22.5°	864.8	916.0	969.4	1026.8	1090.3	1125.2	1158.5	1225.9	1282.5	1329.8	1387.1
25°	842.3	896.6	951.6	1012.0	1083.3	1121.3	1155.4	1222.0	1282.5	1344.5	1400.3
27.5°	819.1	874.9	932.2	995.8	1068.6	1105.8	1144.6	1208.9	1279.4	1346.8	1403.4
30°	793.5	847.8	908.2	968.6	1046.1	1083.3	1122.9	1192.6	1269.3	1336.7	1398.0
32.5°	765.6	821.4	878.8	941.5	1017.5	1057.8	1094.2	1173.2	1251.5	1318.1	1375.5
35°	734.6	787.3	841.6	905.9	981.0	1017.5	1060.9	1143.0	1222.0	1292.6	1329.8
37.5°	701.3	751.7	802.0	865.6	937.7	981.8	1024.4	1107.4	1191.1	1238.3	1257.7
40°	670.3	714.5	758.6	819.9	892.7	938.4	981.8	1067.8	1141.5	1177.9	1163.2
42.5°	630.8	676.5	716.0	772.6	846.2	888.8	933.0	1022.1	1081.8	1096.5	1060.1
45°	592.0	630.0	668.0	723.0	800.5	836.9	884.2	967.1	1016.7	1003.5	950.1
47.5°	554.1	585.1	620.7	674.2	743.9	787.3	831.5	903.6	938.4	919.8	845.4
50°	509.1	540.1	577.3	623.8	691.2	733.1	767.9	834.6	860.9	815.2	725.3
52.5°	466.5	493.6	525.4	568.8	633.1	671.1	709.1	766.4	774.9	722.2	627.7
55°	426.2	447.9	481.2	516.1	575.0	615.3	641.6	690.5	688.1	622.3	540.9
57.5°	384.4	404.5	427.0	463.4	519.2	549.4	578.1	620.7	598.2	542.4	461.9
60°	347.2	358.8	381.3	416.1	463.4	489.7	512.2	535.5	516.1	455.7	393.7
62.5°	306.1	319.3	335.5	363.4	405.3	430.1	446.4	456.4	436.3	389.8	333.2
65°	267.3	279.0	296.0	320.8	352.6	371.2	379.7	386.7	375.8	323.1	278.2
67.5°	232.5	240.2	255.7	272.0	306.1	310.7	322.4	325.5	303.8	263.5	227.8
70°	197.6	205.4	212.3	231.7	247.2	255.7	258.0	258.0	236.4	210.0	180.6
72.5°	165.1	169.7	176.7	189.9	198.4	204.6	207.7	203.8	183.7	162.0	140.3
75°	134.1	136.4	142.6	151.1	158.1	155.8	155.0	150.3	135.6	120.1	107.7
77.5°	103.1	104.6	111.6	113.9	113.9	116.2	113.1	108.5	96.1	84.5	79.0
80°	77.5	79.8	80.6	82.1	80.6	80.6	78.3	70.5	64.3	58.9	55.0
82.5°	53.5	55.0	55.8	53.5	55.0	52.7	48.8	43.4	39.5	38.7	37.2
85°	31.8	32.5	31.8	31.8	29.4	28.7	25.6	24.8	23.2	23.2	22.5
87.5°	15.5	14.7	13.2	11.6	11.6	10.8	11.6	10.1	11.6	10.8	10.1
90°	1.0	3.0	5.9	6.9	7.9	7.9	7.9	13.8	13.8	15.8	17.8
92.5°	13.8	19.8	30.6	45.5	63.3	76.2	89.0	150.2	246.1	339.0	387.4
95°	32.6	35.6	45.5	58.3	82.0	102.8	123.5	209.5	371.6	607.8	805.5
97.5°	54.4	54.4	63.3	75.1	95.9	113.7	131.5	199.6	339.0	582.1	861.8
100°	75.1	75.1	82.0	93.9	112.7	128.5	144.3	202.6	314.3	515.9	794.6
102.5°	94.9	96.9	102.8	113.7	131.5	146.3	161.1	212.5	307.4	471.4	710.6
105°	115.6	118.6	123.5	135.4	153.2	167.6	181.9	229.3	311.3	449.7	648.4
107.5°	138.4	140.3	145.3	158.1	174.9	189.2	203.6	247.1	323.2	443.8	607.8
110°	161.1	163.1	168.0	179.9	197.7	211.0	224.4	267.8	337.0	445.7	589.1

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	182.8	184.8	190.8	201.6	219.4	232.8	246.1	287.6	351.9	451.7	580.2
115°	203.6	206.6	213.5	223.4	242.1	255.4	268.8	308.4	367.7	459.6	578.2
117.5°	225.3	228.3	234.2	245.1	262.9	276.8	290.6	328.1	383.5	467.5	577.2
120°	247.1	249.1	256.0	266.9	283.7	297.5	311.3	348.9	400.3	476.4	577.2
122.5°	266.9	268.8	275.8	285.6	304.4	317.8	331.1	368.7	416.1	485.3	576.2
125°	283.7	287.6	293.5	304.4	323.2	337.0	350.9	386.4	431.9	494.2	575.2
127.5°	299.5	302.4	309.4	321.2	341.0	354.8	368.7	403.3	445.7	501.1	573.2
130°	312.3	316.3	324.2	339.0	357.8	372.1	386.4	420.1	458.6	509.0	572.3
132.5°	325.2	328.1	339.0	352.8	373.6	387.0	400.3	433.9	471.4	515.9	571.3
135°	337.0	341.0	350.9	367.7	388.4	401.2	414.1	446.7	482.3	522.8	570.3
137.5°	348.9	352.8	363.7	379.5	401.3	413.6	426.0	456.6	490.2	526.8	570.3
140°	361.7	364.7	375.6	392.4	413.1	425.0	436.9	466.5	498.1	531.7	569.3
142.5°	375.6	378.5	388.4	404.2	424.0	435.4	446.7	475.4	504.1	535.7	569.3
145°	388.4	391.4	401.3	415.1	433.9	444.8	455.6	481.3	508.0	536.7	567.3
147.5°	403.3	404.2	413.1	428.0	443.8	453.6	463.5	488.2	512.0	537.7	564.4
150°	417.1	418.1	426.0	437.8	452.7	462.0	471.4	493.2	514.9	537.7	561.4
152.5°	429.9	429.9	437.8	448.7	461.6	470.0	478.4	497.1	516.9	535.7	556.4
155°	441.8	442.8	448.7	458.6	469.5	476.9	484.3	501.1	517.9	533.7	551.5
157.5°	453.7	453.7	459.6	467.5	477.4	483.3	489.2	504.1	517.9	531.7	546.6
160°	464.5	464.5	468.5	475.4	483.3	488.8	494.2	506.0	517.9	528.8	540.6
162.5°	474.4	473.4	476.4	482.3	489.2	493.2	497.1	508.0	517.9	525.8	534.7
165°	481.3	481.3	483.3	488.2	493.2	496.2	499.1	508.0	515.9	521.9	528.8
167.5°	489.2	488.2	489.2	493.2	496.2	498.6	501.1	508.0	513.9	517.9	522.8
170°	494.2	493.2	494.2	497.1	499.1	500.6	502.1	507.0	512.0	513.9	516.9
172.5°	499.1	498.1	498.1	500.1	501.1	502.1	503.1	506.0	510.0	510.0	511.0
175°	502.1	501.1	501.1	502.1	503.1	503.1	503.1	505.1	508.0	507.0	507.0
177.5°	504.1	503.1	502.1	503.1	503.1	503.1	503.1	504.1	506.0	504.1	504.1
180°	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	1008.2	1016.7	1017.5	1025.2	1022.9	1019.0	1026.0	1021.3	1030.6	1027.5	1031.4
5°	1067.1	1078.7	1088.8	1095.0	1105.8	1103.5	1115.1	1111.2	1119.8	1111.2	1122.1
7.5°	1136.0	1155.4	1165.5	1181.8	1186.4	1187.2	1201.1	1204.2	1209.6	1204.2	1210.4
10°	1203.4	1226.7	1249.9	1263.1	1271.6	1283.3	1295.7	1301.1	1305.0	1299.5	1303.4
12.5°	1264.7	1301.1	1326.7	1353.0	1359.2	1369.3	1382.5	1380.9	1396.4	1393.3	1400.3
15°	1321.2	1361.5	1392.5	1413.5	1430.5	1439.0	1463.8	1465.4	1464.6	1472.3	1467.7
17.5°	1371.6	1405.7	1449.9	1477.0	1497.9	1497.9	1511.9	1540.5	1538.2	1537.4	1542.1
20°	1412.7	1451.4	1492.5	1538.2	1555.3	1558.4	1577.7	1592.5	1594.8	1594.8	1594.8
22.5°	1443.7	1489.4	1533.6	1566.1	1579.3	1590.1	1607.2	1616.5	1619.6	1618.0	1619.6
25°	1459.2	1502.6	1547.5	1577.0	1584.7	1590.9	1592.5	1597.9	1597.1	1587.8	1593.2
27.5°	1462.3	1504.1	1533.6	1541.3	1537.4	1533.6	1508.8	1511.1	1504.1	1490.2	1495.6
30°	1448.3	1470.8	1470.0	1446.0	1439.0	1422.8	1400.3	1367.0	1339.8	1328.2	1332.1
32.5°	1398.0	1398.0	1370.1	1315.8	1291.8	1262.3	1222.0	1191.8	1156.2	1148.4	1163.2
35°	1328.2	1288.7	1237.5	1166.3	1129.8	1108.1	1038.4	1016.7	986.5	977.9	984.9
37.5°	1219.7	1153.9	1079.5	1012.8	981.8	943.1	881.9	850.9	829.2	814.4	821.4
40°	1098.1	1018.2	940.8	858.6	824.5	792.7	747.0	719.1	684.3	685.8	688.1
42.5°	981.8	888.1	801.3	725.3	692.8	666.4	634.7	600.6	588.2	584.3	580.4
45°	858.6	758.6	677.3	620.7	591.3	566.5	537.0	517.6	502.9	499.8	503.7
47.5°	742.4	657.9	580.4	527.7	503.7	491.3	468.1	450.2	440.9	433.2	437.8
50°	637.0	557.9	495.9	451.8	434.7	426.2	404.5	395.2	385.9	383.6	382.8
52.5°	550.2	482.8	429.3	393.7	380.5	375.8	359.6	346.4	338.6	341.0	342.5
55°	471.2	413.8	372.0	343.3	332.4	327.0	315.4	306.1	300.7	298.3	299.9
57.5°	401.4	351.8	321.6	298.3	289.8	287.5	275.1	272.0	268.1	265.8	265.8
60°	337.9	303.0	275.1	261.9	252.6	250.3	241.0	237.1	236.4	234.0	232.5
62.5°	284.4	255.7	236.4	222.4	218.5	217.8	211.6	206.9	204.6	203.0	203.0
65°	237.9	217.0	200.7	190.6	187.5	186.0	179.0	177.5	175.9	174.4	173.6
67.5°	198.4	179.8	168.2	161.2	157.3	158.1	154.2	151.1	151.1	150.3	149.6
70°	160.4	148.8	138.7	134.8	133.3	131.7	130.2	127.9	127.1	127.1	127.1
72.5°	126.3	118.6	113.1	110.8	109.3	107.7	106.2	106.2	106.2	105.4	105.4
75°	96.9	93.8	89.9	87.6	87.6	89.1	86.8	84.5	82.1	80.6	81.4
77.5°	72.8	71.3	69.0	65.1	65.9	64.3	64.3	62.8	63.5	63.5	62.0
80°	53.5	51.1	50.4	48.0	48.8	48.0	47.3	47.3	45.7	45.7	45.7
82.5°	37.2	34.9	34.9	34.1	33.3	33.3	32.5	32.5	33.3	31.8	31.8
85°	22.5	21.7	21.7	20.1	20.1	20.1	20.1	20.9	20.1	19.4	19.4
87.5°	10.1	10.8	10.1	9.3	9.3	9.3	8.5	8.5	7.7	8.5	8.5
90°	16.8	17.8	18.8	19.8	19.8	19.8	20.8	21.7	20.8	20.8	20.8
92.5°	322.2	238.2	177.9	140.3	128.0	115.6	100.8	93.9	89.9	89.9	89.9
95°	828.2	732.4	579.2	446.7	398.8	350.9	302.4	271.8	254.0	241.2	254.0
97.5°	1038.8	1054.6	978.5	869.8	814.4	759.1	691.9	632.5	602.9	579.2	602.9
100°	1047.7	1192.0	1211.7	1163.3	1126.8	1090.2	1004.2	943.9	914.2	906.3	914.2
102.5°	973.5	1185.0	1302.7	1332.3	1322.4	1312.5	1268.1	1228.5	1196.9	1191.0	1196.9
105°	880.6	1107.0	1277.9	1375.8	1396.0	1416.3	1418.3	1410.4	1396.6	1390.6	1396.6
107.5°	804.5	1011.1	1195.9	1332.3	1373.8	1415.3	1458.8	1476.6	1484.5	1485.5	1484.5
110°	750.2	926.1	1097.1	1240.4	1294.8	1349.1	1419.3	1460.8	1478.6	1487.5	1478.6

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	719.5	863.8	1010.1	1143.5	1197.9	1252.3	1334.3	1386.7	1413.4	1429.2	1413.4
115°	702.7	826.3	947.8	1063.5	1111.0	1158.4	1236.4	1295.7	1327.4	1335.3	1327.4
117.5°	693.8	804.5	907.3	1001.2	1042.7	1084.2	1153.4	1204.8	1238.4	1243.4	1238.4
120°	686.9	790.7	882.6	961.7	996.8	1031.8	1088.2	1131.7	1157.4	1168.2	1157.4
122.5°	679.0	778.8	866.8	937.0	966.6	996.3	1041.7	1077.3	1098.1	1108.9	1098.1
125°	670.1	765.0	850.0	918.2	945.4	972.5	1012.1	1040.7	1059.5	1065.5	1059.5
127.5°	658.2	749.2	831.2	899.4	925.1	950.8	990.3	1016.0	1031.8	1037.8	1031.8
130°	647.4	729.4	807.5	874.7	900.9	927.1	967.6	992.3	1008.1	1014.1	1008.1
132.5°	637.5	708.7	780.8	846.0	872.2	898.4	938.0	966.6	981.4	987.4	981.4
135°	627.6	689.9	754.1	814.4	839.1	863.8	903.4	931.0	946.8	952.8	946.8
137.5°	618.7	672.1	728.4	780.8	803.6	826.3	863.8	892.5	905.3	912.3	905.3
140°	611.8	657.3	703.7	748.2	769.0	789.7	824.3	846.0	859.9	867.8	859.9
142.5°	605.9	643.4	683.0	719.5	736.8	754.1	783.8	803.5	815.4	820.3	815.4
145°	598.9	630.6	664.2	693.8	707.6	721.5	746.2	763.0	772.9	777.8	772.9
147.5°	593.0	619.7	647.4	672.1	683.4	694.8	713.6	728.4	736.3	738.3	736.3
150°	586.1	609.8	632.5	652.3	661.2	670.1	685.9	698.8	704.7	705.7	704.7
152.5°	578.2	598.9	617.7	635.5	642.4	649.4	662.2	672.1	675.0	676.0	675.0
155°	570.3	588.1	603.9	618.7	624.7	630.6	640.5	648.4	651.3	651.3	651.3
157.5°	562.4	576.2	590.1	602.9	607.8	612.8	620.7	626.6	628.6	628.6	628.6
160°	553.5	565.3	576.2	587.1	591.0	595.0	600.9	606.9	607.8	607.8	607.8
162.5°	545.6	554.5	563.4	571.3	574.8	578.2	582.1	588.1	589.1	588.1	589.1
165°	536.7	544.6	550.5	557.4	559.9	562.4	566.3	570.3	569.3	568.3	569.3
167.5°	528.8	534.7	539.6	545.6	547.0	548.5	550.5	553.5	553.5	552.5	553.5
170°	520.9	525.8	528.8	532.7	534.2	535.7	537.7	538.7	537.7	537.7	537.7
172.5°	513.9	517.9	519.9	521.9	522.8	523.8	524.8	525.8	524.8	522.8	524.8
175°	509.0	511.0	512.0	513.9	513.9	513.9	513.9	515.9	513.9	512.0	513.9
177.5°	505.1	506.0	507.0	507.0	507.5	508.0	507.0	508.0	506.0	504.1	506.0
180°	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	1033.7	1028.3	1027.5	1027.5	1019.0	1023.7	1014.4	1004.3	999.6	999.6	991.1
5°	1119.8	1114.3	1108.9	1100.4	1100.4	1095.7	1081.0	1066.3	1055.4	1046.1	1036.1
7.5°	1208.1	1202.7	1187.2	1178.7	1183.3	1174.0	1154.6	1129.8	1111.2	1096.5	1075.6
10°	1304.2	1289.5	1281.7	1277.1	1260.8	1250.7	1228.2	1191.8	1168.6	1149.2	1122.1
12.5°	1382.5	1387.1	1357.7	1360.0	1343.7	1329.8	1294.9	1260.0	1225.1	1198.0	1157.7
15°	1466.9	1453.0	1435.1	1421.2	1415.8	1398.7	1369.3	1322.8	1284.8	1242.2	1196.5
17.5°	1533.6	1522.7	1505.7	1492.5	1480.9	1439.8	1415.0	1373.9	1322.0	1280.2	1224.4
20°	1590.1	1580.1	1556.0	1547.5	1526.6	1497.1	1461.5	1398.0	1351.5	1305.7	1251.5
22.5°	1614.2	1604.1	1583.2	1572.3	1559.1	1530.5	1496.4	1435.9	1378.6	1321.2	1263.9
25°	1594.0	1594.0	1583.9	1580.1	1568.4	1542.9	1508.0	1456.8	1395.6	1333.6	1265.4
27.5°	1496.4	1515.7	1522.7	1526.6	1526.6	1527.4	1503.3	1453.7	1394.1	1333.6	1262.3
30°	1355.3	1387.9	1416.6	1425.1	1439.8	1456.1	1466.1	1442.1	1388.7	1325.1	1253.8
32.5°	1177.9	1219.7	1273.2	1286.4	1306.5	1355.3	1382.5	1392.5	1363.1	1307.3	1231.3
35°	1001.2	1053.9	1086.4	1126.7	1145.3	1217.4	1277.8	1314.3	1307.3	1274.0	1205.0
37.5°	847.0	877.2	916.7	959.3	996.5	1065.5	1140.7	1211.2	1239.9	1223.6	1171.7
40°	699.0	734.6	781.9	816.8	842.3	911.3	1004.3	1081.0	1143.8	1153.9	1122.1
42.5°	594.4	630.0	658.7	696.7	716.8	783.4	865.6	961.7	1036.1	1075.6	1061.6
45°	513.8	535.5	558.7	580.4	605.2	664.1	740.0	845.4	929.1	984.9	990.3
47.5°	443.3	462.6	482.8	502.9	516.9	562.6	632.3	718.3	809.8	886.5	916.7
50°	393.7	403.0	417.7	429.3	445.6	485.1	540.9	615.3	712.2	795.1	834.6
52.5°	344.8	356.5	368.1	378.2	389.0	416.9	468.1	532.4	616.1	701.3	750.1
55°	303.8	313.1	323.9	330.9	337.1	361.9	400.6	450.2	522.3	602.9	663.3
57.5°	270.4	274.3	283.6	287.5	294.5	314.6	342.5	386.7	444.8	523.1	572.7
60°	234.0	241.8	248.7	251.8	257.3	271.2	290.6	331.7	382.0	439.4	495.9
62.5°	204.6	207.7	213.1	217.0	220.9	235.6	251.8	282.8	320.8	368.9	420.8
65°	177.5	179.0	182.1	187.5	189.9	200.7	210.0	232.5	268.1	304.5	356.5
67.5°	149.6	151.1	155.0	158.1	160.4	167.4	177.5	193.7	213.1	253.4	282.1
70°	127.9	127.9	130.2	131.7	134.1	137.2	142.6	155.0	172.8	198.4	224.7
72.5°	106.9	106.9	106.9	109.3	109.3	111.6	114.7	123.2	135.6	155.8	172.8
75°	82.9	83.7	85.2	85.2	86.0	89.1	91.4	93.8	100.0	113.1	128.6
77.5°	62.8	64.3	65.1	63.5	65.1	65.1	68.2	71.3	74.4	78.3	89.9
80°	46.5	47.3	45.7	46.5	46.5	48.0	49.6	48.8	50.4	55.0	58.1
82.5°	31.0	31.8	31.8	31.8	31.8	34.1	34.1	33.3	34.1	34.9	35.6
85°	19.4	18.6	18.6	19.4	18.6	18.6	19.4	20.1	19.4	20.1	20.9
87.5°	8.5	8.5	8.5	8.5	7.7	7.7	8.5	7.7	8.5	7.7	7.0
90°	21.7	20.8	19.8	19.8	19.8	18.8	17.8	16.8	17.8	15.8	13.8
92.5°	93.9	100.8	115.6	128.0	140.3	177.9	238.2	322.2	387.4	339.0	246.1
95°	271.8	302.4	350.9	398.8	446.7	579.2	732.4	828.2	805.5	607.8	371.6
97.5°	632.5	691.9	759.1	814.4	869.8	978.5	1054.6	1038.8	861.8	582.1	339.0
100°	943.9	1004.2	1090.2	1126.8	1163.3	1211.7	1192.0	1047.7	794.6	515.9	314.3
102.5°	1228.5	1268.1	1312.5	1322.4	1332.3	1302.7	1185.0	973.5	710.6	471.4	307.4
105°	1410.4	1418.3	1416.3	1396.0	1375.8	1277.9	1107.0	880.6	648.4	449.7	311.3
107.5°	1476.6	1458.8	1415.3	1373.8	1332.3	1195.9	1011.1	804.5	607.8	443.8	323.2
110°	1460.8	1419.3	1349.1	1294.8	1240.4	1097.1	926.1	750.2	589.1	445.7	337.0

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1386.7	1334.3	1252.3	1197.9	1143.5	1010.1	863.8	719.5	580.2	451.7	351.9
115°	1295.7	1236.4	1158.4	1111.0	1063.5	947.8	826.3	702.7	578.2	459.6	367.7
117.5°	1204.8	1153.4	1084.2	1042.7	1001.2	907.3	804.5	693.8	577.2	467.5	383.5
120°	1131.7	1088.2	1031.8	996.8	961.7	882.6	790.7	686.9	577.2	476.4	400.3
122.5°	1077.3	1041.7	996.3	966.6	937.0	866.8	778.8	679.0	576.2	485.3	416.1
125°	1040.7	1012.1	972.5	945.4	918.2	850.0	765.0	670.1	575.2	494.2	431.9
127.5°	1016.0	990.3	950.8	925.1	899.4	831.2	749.2	658.2	573.2	501.1	445.7
130°	992.3	967.6	927.1	900.9	874.7	807.5	729.4	647.4	572.3	509.0	458.6
132.5°	966.6	938.0	898.4	872.2	846.0	780.8	708.7	637.5	571.3	515.9	471.4
135°	931.0	903.4	863.8	839.1	814.4	754.1	689.9	627.6	570.3	522.8	482.3
137.5°	892.5	863.8	826.3	803.6	780.8	728.4	672.1	618.7	570.3	526.8	490.2
140°	846.0	824.3	789.7	769.0	748.2	703.7	657.3	611.8	569.3	531.7	498.1
142.5°	803.5	783.8	754.1	736.8	719.5	683.0	643.4	605.9	569.3	535.7	504.1
145°	763.0	746.2	721.5	707.6	693.8	664.2	630.6	598.9	567.3	536.7	508.0
147.5°	728.4	713.6	694.8	683.4	672.1	647.4	619.7	593.0	564.4	537.7	512.0
150°	698.8	685.9	670.1	661.2	652.3	632.5	609.8	586.1	561.4	537.7	514.9
152.5°	672.1	662.2	649.4	642.4	635.5	617.7	598.9	578.2	556.4	535.7	516.9
155°	648.4	640.5	630.6	624.7	618.7	603.9	588.1	570.3	551.5	533.7	517.9
157.5°	626.6	620.7	612.8	607.8	602.9	590.1	576.2	562.4	546.6	531.7	517.9
160°	606.9	600.9	595.0	591.0	587.1	576.2	565.3	553.5	540.6	528.8	517.9
162.5°	588.1	582.1	578.2	574.8	571.3	563.4	554.5	545.6	534.7	525.8	517.9
165°	570.3	566.3	562.4	559.9	557.4	550.5	544.6	536.7	528.8	521.9	515.9
167.5°	553.5	550.5	548.5	547.0	545.6	539.6	534.7	528.8	522.8	517.9	513.9
170°	538.7	537.7	535.7	534.2	532.7	528.8	525.8	520.9	516.9	513.9	512.0
172.5°	525.8	524.8	523.8	522.8	521.9	519.9	517.9	513.9	511.0	510.0	510.0
175°	515.9	513.9	513.9	513.9	513.9	512.0	511.0	509.0	507.0	507.0	508.0
177.5°	508.0	507.0	508.0	507.5	507.0	507.0	506.0	505.1	504.1	504.1	506.0
180°	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	986.5	982.6	980.3	979.5	972.5	968.6	966.3	964.8	962.4	956.2	950.8
5°	1023.7	1012.8	1007.4	1001.2	990.3	977.9	967.9	961.7	953.9	941.5	929.9
7.5°	1058.5	1042.3	1031.4	1022.9	1004.3	984.1	967.9	954.7	940.0	922.9	906.7
10°	1095.0	1068.6	1054.7	1041.5	1014.4	988.0	964.8	945.4	924.5	902.0	884.2
12.5°	1123.6	1088.8	1073.3	1054.7	1021.3	990.3	960.9	934.6	907.4	883.4	857.8
15°	1157.0	1113.6	1095.7	1071.7	1026.0	985.7	947.7	919.1	891.2	855.5	828.4
17.5°	1176.3	1126.0	1100.4	1079.5	1029.9	981.0	936.9	901.2	868.7	833.0	804.4
20°	1195.7	1138.4	1109.7	1080.2	1021.3	969.4	922.9	880.3	846.2	807.5	778.0
22.5°	1201.9	1135.3	1105.0	1077.9	1015.9	957.8	904.3	860.9	821.4	782.7	749.3
25°	1201.9	1134.5	1098.8	1064.0	998.9	939.2	885.7	838.5	794.3	755.5	722.2
27.5°	1189.5	1119.0	1081.8	1050.0	982.6	918.3	863.3	811.3	768.7	730.0	692.0
30°	1174.0	1096.5	1059.3	1021.3	956.2	895.0	835.4	787.3	742.4	698.2	664.1
32.5°	1154.6	1072.5	1031.4	992.7	923.7	860.2	805.1	757.9	715.3	669.5	631.6
35°	1126.7	1036.8	991.1	957.0	890.4	824.5	771.8	725.3	684.3	637.0	595.9
37.5°	1091.1	1004.3	957.8	916.0	847.0	786.5	736.9	692.0	651.7	608.3	562.6
40°	1049.2	958.6	918.3	874.1	801.3	743.9	697.4	657.1	616.8	575.8	531.6
42.5°	1002.0	912.1	867.1	824.5	754.8	698.2	654.8	618.4	581.2	543.2	495.9
45°	945.4	860.9	817.5	777.2	709.8	651.7	612.2	577.3	545.5	506.8	465.0
47.5°	881.9	808.2	764.1	720.7	654.8	604.4	565.7	536.2	509.1	470.4	432.4
50°	819.9	747.0	711.4	667.2	606.8	559.5	520.0	495.2	474.3	436.3	402.2
52.5°	741.6	686.6	652.5	614.5	556.4	508.3	477.4	455.7	430.9	401.4	371.2
55°	672.6	621.5	594.4	558.7	501.4	458.8	432.4	412.3	392.9	366.5	342.5
57.5°	594.4	562.6	535.5	504.5	447.9	411.5	388.2	371.2	353.4	331.7	312.3
60°	512.2	497.5	471.2	446.4	398.3	366.5	347.2	331.7	314.6	296.8	280.5
62.5°	439.4	430.9	415.4	396.0	351.0	323.9	304.5	292.9	280.5	264.2	248.7
65°	370.4	366.5	351.8	337.9	306.9	282.8	265.8	258.8	244.9	232.5	218.5
67.5°	309.2	304.5	296.0	289.8	263.5	241.0	232.5	223.2	211.6	202.3	190.6
70°	247.2	246.4	241.0	233.3	219.3	203.0	194.5	188.3	176.7	169.7	161.2
72.5°	192.2	196.1	191.4	188.3	179.0	167.4	159.6	155.8	146.5	141.0	134.8
75°	143.4	146.5	148.8	143.4	141.0	135.6	128.6	124.8	120.1	112.4	110.0
77.5°	97.6	104.6	104.6	106.2	106.9	103.8	98.4	95.3	89.9	88.3	85.2
80°	64.3	70.5	71.3	72.8	75.2	75.2	71.3	70.5	65.1	64.3	62.0
82.5°	37.2	42.6	45.7	48.0	47.3	50.4	47.3	46.5	43.4	43.4	41.8
85°	20.1	20.9	22.5	24.0	25.6	27.1	27.1	26.3	25.6	24.8	23.2
87.5°	7.7	7.7	8.5	7.7	8.5	10.1	10.8	10.8	10.1	9.3	7.7
90°	13.8	7.9	7.9	7.9	6.9	5.9	3.0	1.0	3.0	5.9	6.9
92.5°	150.2	89.0	76.2	63.3	45.5	30.6	19.8	13.8	19.8	30.6	45.5
95°	209.5	123.5	102.8	82.0	58.3	45.5	35.6	32.6	35.6	45.5	58.3
97.5°	199.6	131.5	113.7	95.9	75.1	63.3	54.4	54.4	54.4	63.3	75.1
100°	202.6	144.3	128.5	112.7	93.9	82.0	75.1	75.1	75.1	82.0	93.9
102.5°	212.5	161.1	146.3	131.5	113.7	102.8	96.9	94.9	96.9	102.8	113.7
105°	229.3	181.9	167.6	153.2	135.4	123.5	118.6	115.6	118.6	123.5	135.4
107.5°	247.1	203.6	189.2	174.9	158.1	145.3	140.3	138.4	140.3	145.3	158.1
110°	267.8	224.4	211.0	197.7	179.9	168.0	163.1	161.1	163.1	168.0	179.9

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	287.6	246.1	232.8	219.4	201.6	190.8	184.8	182.8	184.8	190.8	201.6
115°	308.4	268.8	255.4	242.1	223.4	213.5	206.6	203.6	206.6	213.5	223.4
117.5°	328.1	290.6	276.8	262.9	245.1	234.2	228.3	225.3	228.3	234.2	245.1
120°	348.9	311.3	297.5	283.7	266.9	256.0	249.1	247.1	249.1	256.0	266.9
122.5°	368.7	331.1	317.8	304.4	285.6	275.8	268.8	266.9	268.8	275.8	285.6
125°	386.4	350.9	337.0	323.2	304.4	293.5	287.6	283.7	287.6	293.5	304.4
127.5°	403.3	368.7	354.8	341.0	321.2	309.4	302.4	299.5	302.4	309.4	321.2
130°	420.1	386.4	372.1	357.8	339.0	324.2	316.3	312.3	316.3	324.2	339.0
132.5°	433.9	400.3	387.0	373.6	352.8	339.0	328.1	325.2	328.1	339.0	352.8
135°	446.7	414.1	401.2	388.4	367.7	350.9	341.0	337.0	341.0	350.9	367.7
137.5°	456.6	426.0	413.6	401.3	379.5	363.7	352.8	348.9	352.8	363.7	379.5
140°	466.5	436.9	425.0	413.1	392.4	375.6	364.7	361.7	364.7	375.6	392.4
142.5°	475.4	446.7	435.4	424.0	404.2	388.4	378.5	375.6	378.5	388.4	404.2
145°	481.3	455.6	444.8	433.9	415.1	401.3	391.4	388.4	391.4	401.3	415.1
147.5°	488.2	463.5	453.6	443.8	428.0	413.1	404.2	403.3	404.2	413.1	428.0
150°	493.2	471.4	462.0	452.7	437.8	426.0	418.1	417.1	418.1	426.0	437.8
152.5°	497.1	478.4	470.0	461.6	448.7	437.8	429.9	429.9	429.9	437.8	448.7
155°	501.1	484.3	476.9	469.5	458.6	448.7	442.8	441.8	442.8	448.7	458.6
157.5°	504.1	489.2	483.3	477.4	467.5	459.6	453.7	453.7	453.7	459.6	467.5
160°	506.0	494.2	488.8	483.3	475.4	468.5	464.5	464.5	464.5	468.5	475.4
162.5°	508.0	497.1	493.2	489.2	482.3	476.4	473.4	474.4	473.4	476.4	482.3
165°	508.0	499.1	496.2	493.2	488.2	483.3	481.3	481.3	481.3	483.3	488.2
167.5°	508.0	501.1	498.6	496.2	493.2	489.2	488.2	489.2	488.2	489.2	493.2
170°	507.0	502.1	500.6	499.1	497.1	494.2	493.2	494.2	493.2	494.2	497.1
172.5°	506.0	503.1	502.1	501.1	500.1	498.1	498.1	499.1	498.1	498.1	500.1
175°	505.1	503.1	503.1	503.1	502.1	501.1	501.1	502.1	501.1	501.1	502.1
177.5°	504.1	503.1	503.1	503.1	503.1	502.1	503.1	504.1	503.1	502.1	503.1
180°	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	946.2	944.6	943.1	936.9	931.5	922.2	914.4	911.3	910.5	911.3	909.0
5°	919.1	918.3	912.9	902.0	891.9	881.1	873.3	865.6	860.9	860.9	855.5
7.5°	893.5	888.1	883.4	869.5	857.8	843.1	831.5	824.5	820.6	812.1	812.1
10°	866.4	858.6	852.4	839.2	822.2	807.5	792.7	784.2	777.2	771.0	768.7
12.5°	839.2	833.0	821.4	807.5	790.4	771.8	756.3	750.1	733.8	720.7	721.4
15°	813.7	799.7	794.3	774.1	754.0	736.2	713.7	695.9	682.7	674.2	663.3
17.5°	785.0	771.0	761.0	743.9	717.6	689.7	668.0	644.0	630.8	616.1	609.1
20°	753.2	741.6	733.8	706.7	675.0	641.6	617.6	602.9	588.2	577.3	571.1
22.5°	726.1	711.4	702.1	665.7	630.8	597.5	578.9	566.5	554.1	544.8	541.7
25°	691.2	682.7	660.2	628.5	585.8	563.4	547.1	530.8	523.8	517.6	510.7
27.5°	662.6	641.6	626.1	584.3	557.9	532.4	516.1	503.7	495.2	489.0	483.5
30°	626.9	607.5	585.8	551.0	526.9	502.9	488.2	478.1	468.8	465.0	460.3
32.5°	589.7	571.9	551.0	523.1	493.6	475.0	463.4	452.6	446.4	442.5	437.1
35°	556.4	533.9	520.0	493.6	469.6	448.7	437.8	428.5	421.6	420.0	419.2
37.5°	520.7	503.7	490.5	463.4	443.3	425.4	415.4	405.3	401.4	400.6	397.5
40°	489.7	475.0	462.6	437.1	415.4	399.1	391.3	385.1	381.3	381.3	380.5
42.5°	462.6	447.1	434.7	411.5	392.1	377.4	368.9	362.7	361.1	361.9	361.1
45°	432.4	419.2	406.8	382.8	366.5	355.7	346.4	343.3	341.0	341.7	342.5
47.5°	403.7	392.9	380.5	361.1	342.5	330.9	325.5	322.4	322.4	322.4	323.9
50°	378.2	365.8	354.9	334.8	317.7	308.4	303.8	299.9	300.7	301.4	302.2
52.5°	347.9	337.1	329.3	309.2	296.8	285.2	279.7	280.5	279.7	279.7	281.3
55°	321.6	310.7	303.0	284.4	272.0	264.2	259.6	257.3	258.0	256.5	259.6
57.5°	292.1	282.8	277.4	259.6	248.7	241.8	237.9	234.0	235.6	234.8	234.0
60°	266.6	255.7	247.2	234.8	225.5	217.0	214.7	210.8	212.3	210.8	210.0
62.5°	237.1	228.6	222.4	210.0	202.3	195.3	189.9	187.5	186.8	184.4	182.1
65°	207.7	203.0	196.8	184.4	176.7	171.3	168.2	165.8	165.1	158.9	151.9
67.5°	180.6	177.5	171.3	162.0	155.0	149.6	144.9	141.0	136.4	131.7	127.9
70°	155.0	150.3	146.5	137.9	131.7	126.3	121.7	117.0	114.7	110.0	108.5
72.5°	130.2	125.5	121.7	113.9	108.5	103.1	101.5	96.1	93.8	93.0	93.0
75°	104.6	100.7	98.4	91.4	86.8	82.9	80.6	79.0	77.5	75.9	73.6
77.5°	79.8	77.5	75.9	71.3	67.4	65.1	64.3	58.9	57.3	55.8	54.2
80°	58.1	57.3	55.8	51.9	50.4	44.9	44.9	43.4	42.6	42.6	42.6
82.5°	39.5	38.0	37.2	33.3	32.5	31.8	31.0	30.2	31.0	30.2	31.0
85°	20.9	20.1	19.4	19.4	19.4	19.4	19.4	19.4	19.4	18.6	19.4
87.5°	7.7	7.7	7.7	7.7	7.0	7.7	7.7	7.0	7.7	7.7	7.7
90°	7.9	7.9	7.9	13.8	13.8	15.8	17.8	16.8	17.8	18.8	19.8
92.5°	63.3	76.2	89.0	150.2	246.1	339.0	387.4	322.2	238.2	177.9	140.3
95°	82.0	102.8	123.5	209.5	371.6	607.8	805.5	828.2	732.4	579.2	446.7
97.5°	95.9	113.7	131.5	199.6	339.0	582.1	861.8	1038.8	1054.6	978.5	869.8
100°	112.7	128.5	144.3	202.6	314.3	515.9	794.6	1047.7	1192.0	1211.7	1163.3
102.5°	131.5	146.3	161.1	212.5	307.4	471.4	710.6	973.5	1185.0	1302.7	1332.3
105°	153.2	167.6	181.9	229.3	311.3	449.7	648.4	880.6	1107.0	1277.9	1375.8
107.5°	174.9	189.2	203.6	247.1	323.2	443.8	607.8	804.5	1011.1	1195.9	1332.3
110°	197.7	211.0	224.4	267.8	337.0	445.7	589.1	750.2	926.1	1097.1	1240.4

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	219.4	232.8	246.1	287.6	351.9	451.7	580.2	719.5	863.8	1010.1	1143.5
115°	242.1	255.4	268.8	308.4	367.7	459.6	578.2	702.7	826.3	947.8	1063.5
117.5°	262.9	276.8	290.6	328.1	383.5	467.5	577.2	693.8	804.5	907.3	1001.2
120°	283.7	297.5	311.3	348.9	400.3	476.4	577.2	686.9	790.7	882.6	961.7
122.5°	304.4	317.8	331.1	368.7	416.1	485.3	576.2	679.0	778.8	866.8	937.0
125°	323.2	337.0	350.9	386.4	431.9	494.2	575.2	670.1	765.0	850.0	918.2
127.5°	341.0	354.8	368.7	403.3	445.7	501.1	573.2	658.2	749.2	831.2	899.4
130°	357.8	372.1	386.4	420.1	458.6	509.0	572.3	647.4	729.4	807.5	874.7
132.5°	373.6	387.0	400.3	433.9	471.4	515.9	571.3	637.5	708.7	780.8	846.0
135°	388.4	401.2	414.1	446.7	482.3	522.8	570.3	627.6	689.9	754.1	814.4
137.5°	401.3	413.6	426.0	456.6	490.2	526.8	570.3	618.7	672.1	728.4	780.8
140°	413.1	425.0	436.9	466.5	498.1	531.7	569.3	611.8	657.3	703.7	748.2
142.5°	424.0	435.4	446.7	475.4	504.1	535.7	569.3	605.9	643.4	683.0	719.5
145°	433.9	444.8	455.6	481.3	508.0	536.7	567.3	598.9	630.6	664.2	693.8
147.5°	443.8	453.6	463.5	488.2	512.0	537.7	564.4	593.0	619.7	647.4	672.1
150°	452.7	462.0	471.4	493.2	514.9	537.7	561.4	586.1	609.8	632.5	652.3
152.5°	461.6	470.0	478.4	497.1	516.9	535.7	556.4	578.2	598.9	617.7	635.5
155°	469.5	476.9	484.3	501.1	517.9	533.7	551.5	570.3	588.1	603.9	618.7
157.5°	477.4	483.3	489.2	504.1	517.9	531.7	546.6	562.4	576.2	590.1	602.9
160°	483.3	488.8	494.2	506.0	517.9	528.8	540.6	553.5	565.3	576.2	587.1
162.5°	489.2	493.2	497.1	508.0	517.9	525.8	534.7	545.6	554.5	563.4	571.3
165°	493.2	496.2	499.1	508.0	515.9	521.9	528.8	536.7	544.6	550.5	557.4
167.5°	496.2	498.6	501.1	508.0	513.9	517.9	522.8	528.8	534.7	539.6	545.6
170°	499.1	500.6	502.1	507.0	512.0	513.9	516.9	520.9	525.8	528.8	532.7
172.5°	501.1	502.1	503.1	506.0	510.0	510.0	511.0	513.9	517.9	519.9	521.9
175°	503.1	503.1	503.1	505.1	508.0	507.0	507.0	509.0	511.0	512.0	513.9
177.5°	503.1	503.1	503.1	504.1	506.0	504.1	504.1	505.1	506.0	507.0	507.0
180°	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	909.0	912.1	908.2	910.5	905.1	904.3	905.1	905.1	905.9	906.7	907.4
5°	857.8	857.1	852.4	849.3	847.0	849.3	850.9	852.4	850.9	852.4	853.2
7.5°	809.8	807.5	805.1	799.7	801.3	799.7	804.4	802.0	802.0	805.9	809.0
10°	767.2	762.5	761.0	754.8	750.1	749.3	754.8	757.1	759.4	761.0	767.2
12.5°	712.2	705.2	699.8	702.1	688.9	694.3	695.9	692.8	702.1	712.9	706.7
15°	653.3	654.0	643.2	639.3	628.5	631.6	632.3	640.1	647.8	647.1	656.4
17.5°	609.9	605.2	595.9	595.1	590.5	592.8	592.0	598.2	595.9	599.8	607.5
20°	569.6	566.5	558.7	555.6	557.2	555.6	556.4	557.2	559.5	568.0	566.5
22.5°	537.8	533.9	533.9	530.0	525.4	523.8	527.7	530.0	533.1	534.7	538.6
25°	509.9	506.8	502.9	500.6	496.7	497.5	499.8	502.9	505.2	508.3	511.4
27.5°	481.2	481.2	477.4	476.6	475.0	474.3	477.4	478.9	478.9	481.2	484.3
30°	458.8	458.8	454.9	454.1	453.3	453.3	455.7	456.4	457.2	459.5	461.1
32.5°	437.1	436.3	434.7	435.5	434.7	435.5	435.5	436.3	437.8	438.6	441.7
35°	416.9	417.7	416.1	416.1	415.4	416.1	417.7	418.5	419.2	420.8	420.8
37.5°	397.5	399.1	398.3	400.6	400.6	400.6	400.6	402.2	402.2	402.2	401.4
40°	380.5	380.5	379.7	381.3	382.8	382.8	383.6	383.6	384.4	384.4	383.6
42.5°	361.1	362.7	365.0	365.8	367.3	366.5	368.9	368.1	368.9	367.3	365.8
45°	343.3	343.3	346.4	349.5	350.3	350.3	350.3	351.8	350.3	347.9	347.2
47.5°	323.9	325.5	327.0	330.9	331.7	331.7	331.7	331.7	330.1	330.1	330.1
50°	304.5	305.3	306.1	307.6	310.0	309.2	309.2	309.2	312.3	309.2	310.0
52.5°	281.3	282.1	282.8	285.9	285.2	285.2	285.9	285.9	288.3	287.5	285.9
55°	258.0	258.0	259.6	259.6	259.6	261.1	261.9	263.5	262.7	263.5	264.2
57.5°	234.8	233.3	232.5	232.5	234.8	234.0	234.8	234.8	237.9	239.4	240.2
60°	207.7	207.7	206.9	202.3	202.3	201.5	203.8	205.4	206.9	213.9	213.1
62.5°	179.8	176.7	173.6	174.4	169.7	172.0	170.5	172.0	176.7	182.1	182.9
65°	151.9	149.6	146.5	145.7	144.1	146.5	145.7	146.5	148.8	151.9	155.8
67.5°	127.1	126.3	124.8	124.0	124.0	124.0	125.5	125.5	126.3	128.6	131.0
70°	108.5	107.7	108.5	106.9	107.7	106.9	107.7	108.5	109.3	110.0	112.4
72.5°	91.4	91.4	91.4	89.9	91.4	90.7	90.7	91.4	92.2	93.0	94.5
75°	72.8	71.3	69.7	68.2	67.4	69.0	69.7	69.0	71.3	74.4	74.4
77.5°	55.0	54.2	54.2	54.2	55.0	54.2	55.8	55.0	55.8	55.8	57.3
80°	42.6	41.8	42.6	42.6	41.8	43.4	42.6	42.6	43.4	44.2	43.4
82.5°	31.0	31.8	31.0	31.0	31.0	32.5	31.0	31.0	31.0	31.8	31.8
85°	19.4	19.4	19.4	19.4	20.1	19.4	20.1	19.4	20.9	20.1	20.1
87.5°	7.0	7.7	8.5	8.5	8.5	8.5	7.7	8.5	9.3	8.5	9.3
90°	19.8	19.8	20.8	21.7	20.8	20.8	20.8	21.7	20.8	19.8	19.8
92.5°	128.0	115.6	100.8	93.9	89.9	89.9	89.9	93.9	100.8	115.6	128.0
95°	398.8	350.9	302.4	271.8	254.0	241.2	254.0	271.8	302.4	350.9	398.8
97.5°	814.4	759.1	691.9	632.5	602.9	579.2	602.9	632.5	691.9	759.1	814.4
100°	1126.8	1090.2	1004.2	943.9	914.2	906.3	914.2	943.9	1004.2	1090.2	1126.8
102.5°	1322.4	1312.5	1268.1	1228.5	1196.9	1191.0	1196.9	1228.5	1268.1	1312.5	1322.4
105°	1396.0	1416.3	1418.3	1410.4	1396.6	1390.6	1396.6	1410.4	1418.3	1416.3	1396.0
107.5°	1373.8	1415.3	1458.8	1476.6	1484.5	1485.5	1484.5	1476.6	1458.8	1415.3	1373.8
110°	1294.8	1349.1	1419.3	1460.8	1478.6	1487.5	1478.6	1460.8	1419.3	1349.1	1294.8

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1197.9	1252.3	1334.3	1386.7	1413.4	1429.2	1413.4	1386.7	1334.3	1252.3	1197.9
115°	1111.0	1158.4	1236.4	1295.7	1327.4	1335.3	1327.4	1295.7	1236.4	1158.4	1111.0
117.5°	1042.7	1084.2	1153.4	1204.8	1238.4	1243.4	1238.4	1204.8	1153.4	1084.2	1042.7
120°	996.8	1031.8	1088.2	1131.7	1157.4	1168.2	1157.4	1131.7	1088.2	1031.8	996.8
122.5°	966.6	996.3	1041.7	1077.3	1098.1	1108.9	1098.1	1077.3	1041.7	996.3	966.6
125°	945.4	972.5	1012.1	1040.7	1059.5	1065.5	1059.5	1040.7	1012.1	972.5	945.4
127.5°	925.1	950.8	990.3	1016.0	1031.8	1037.8	1031.8	1016.0	990.3	950.8	925.1
130°	900.9	927.1	967.6	992.3	1008.1	1014.1	1008.1	992.3	967.6	927.1	900.9
132.5°	872.2	898.4	938.0	966.6	981.4	987.4	981.4	966.6	938.0	898.4	872.2
135°	839.1	863.8	903.4	931.0	946.8	952.8	946.8	931.0	903.4	863.8	839.1
137.5°	803.6	826.3	863.8	892.5	905.3	912.3	905.3	892.5	863.8	826.3	803.6
140°	769.0	789.7	824.3	846.0	859.9	867.8	859.9	846.0	824.3	789.7	769.0
142.5°	736.8	754.1	783.8	803.5	815.4	820.3	815.4	803.5	783.8	754.1	736.8
145°	707.6	721.5	746.2	763.0	772.9	777.8	772.9	763.0	746.2	721.5	707.6
147.5°	683.4	694.8	713.6	728.4	736.3	738.3	736.3	728.4	713.6	694.8	683.4
150°	661.2	670.1	685.9	698.8	704.7	705.7	704.7	698.8	685.9	670.1	661.2
152.5°	642.4	649.4	662.2	672.1	675.0	676.0	675.0	672.1	662.2	649.4	642.4
155°	624.7	630.6	640.5	648.4	651.3	651.3	651.3	648.4	640.5	630.6	624.7
157.5°	607.8	612.8	620.7	626.6	628.6	628.6	628.6	626.6	620.7	612.8	607.8
160°	591.0	595.0	600.9	606.9	607.8	607.8	607.8	606.9	600.9	595.0	591.0
162.5°	574.8	578.2	582.1	588.1	589.1	588.1	589.1	588.1	582.1	578.2	574.8
165°	559.9	562.4	566.3	570.3	569.3	568.3	569.3	570.3	566.3	562.4	559.9
167.5°	547.0	548.5	550.5	553.5	553.5	552.5	553.5	553.5	550.5	548.5	547.0
170°	534.2	535.7	537.7	538.7	537.7	537.7	537.7	538.7	537.7	535.7	534.2
172.5°	522.8	523.8	524.8	525.8	524.8	522.8	524.8	525.8	524.8	523.8	522.8
175°	513.9	513.9	513.9	515.9	513.9	512.0	513.9	515.9	513.9	513.9	513.9
177.5°	507.5	508.0	507.0	508.0	506.0	504.1	506.0	508.0	507.0	508.0	507.5
180°	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	910.5	914.4	912.9	907.4	909.8	914.4	919.1	925.3	929.1	932.2	933.8
5°	857.1	864.0	862.5	862.5	865.6	873.3	881.1	894.3	898.9	904.3	912.1
7.5°	809.8	815.2	819.9	821.4	826.1	836.1	846.2	860.9	872.6	878.8	883.4
10°	767.9	771.8	778.8	782.7	787.3	799.7	814.4	829.9	841.6	852.4	858.6
12.5°	714.5	730.0	739.3	745.5	751.7	770.3	781.9	798.9	812.9	823.0	832.3
15°	654.8	673.4	678.8	702.9	718.3	733.1	750.9	771.0	784.2	795.8	808.2
17.5°	604.4	617.6	623.8	649.4	662.6	685.8	711.4	736.9	757.1	765.6	778.0
20°	572.7	579.6	592.0	600.6	614.5	641.6	669.5	700.5	730.7	739.3	751.7
22.5°	540.1	549.4	557.9	569.6	580.4	599.0	626.9	661.0	693.6	709.1	723.8
25°	510.7	520.0	525.4	537.8	547.9	566.5	585.8	620.7	659.5	672.6	695.9
27.5°	487.4	492.8	502.1	507.6	519.2	536.2	554.1	580.4	618.4	640.9	663.3
30°	464.2	468.1	475.8	483.5	492.1	503.7	523.8	549.4	584.3	603.7	626.1
32.5°	440.9	447.1	451.8	457.2	466.5	480.4	494.4	519.2	547.1	568.8	591.3
35°	421.6	423.9	430.1	436.3	442.5	454.9	469.6	493.6	518.4	535.5	555.6
37.5°	400.6	404.5	409.2	411.5	421.6	429.3	444.8	463.4	492.8	503.7	523.8
40°	384.4	383.6	388.2	392.1	396.8	409.2	418.5	438.6	461.9	478.9	491.3
42.5°	364.2	364.2	365.8	370.4	376.6	384.4	395.2	412.3	436.3	448.7	463.4
45°	347.9	345.6	346.4	349.5	353.4	361.1	372.0	386.7	410.7	420.8	436.3
47.5°	328.6	326.2	326.2	329.3	332.4	337.9	346.4	363.4	382.8	396.0	407.6
50°	306.9	307.6	306.9	309.2	310.7	316.2	325.5	339.4	357.2	368.1	381.3
52.5°	286.7	285.2	284.4	285.9	289.0	292.9	303.0	315.4	332.4	343.3	354.9
55°	261.9	263.5	263.5	263.5	268.1	269.7	277.4	289.8	306.9	315.4	326.2
57.5°	239.4	238.7	240.2	239.4	243.3	248.7	254.9	264.2	281.3	289.8	299.9
60°	214.7	215.4	216.2	216.2	219.3	224.7	231.7	240.2	254.2	262.7	272.0
62.5°	184.4	188.3	192.2	193.7	198.4	202.3	206.9	216.2	228.6	234.8	243.3
65°	155.8	161.2	166.6	170.5	173.6	177.5	183.7	192.2	202.3	208.5	217.0
67.5°	131.0	134.8	141.8	145.7	151.9	156.5	160.4	167.4	179.8	182.1	189.1
70°	113.1	114.7	117.8	120.9	127.9	131.7	136.4	143.4	152.7	158.1	162.0
72.5°	95.3	96.1	97.6	100.7	103.8	108.5	113.9	120.1	128.6	131.0	136.4
75°	75.9	80.6	80.6	82.9	85.2	87.6	92.2	98.4	103.8	107.7	110.8
77.5°	56.6	58.9	60.4	64.3	67.4	69.7	72.8	77.5	80.6	83.7	86.0
80°	44.2	44.9	45.7	45.7	47.3	50.4	53.5	56.6	60.4	62.0	64.3
82.5°	32.5	32.5	32.5	34.1	34.9	35.6	35.6	37.2	41.1	42.6	44.9
85°	20.9	20.9	20.9	20.9	21.7	22.5	23.2	24.0	24.0	24.0	25.6
87.5°	8.5	10.1	9.3	10.1	10.1	10.1	10.1	10.8	10.8	11.6	11.6
90°	19.8	18.8	17.8	16.8	17.8	15.8	13.8	13.8	7.9	7.9	7.9
92.5°	140.3	177.9	238.2	322.2	387.4	339.0	246.1	150.2	89.0	76.2	63.3
95°	446.7	579.2	732.4	828.2	805.5	607.8	371.6	209.5	123.5	102.8	82.0
97.5°	869.8	978.5	1054.6	1038.8	861.8	582.1	339.0	199.6	131.5	113.7	95.9
100°	1163.3	1211.7	1192.0	1047.7	794.6	515.9	314.3	202.6	144.3	128.5	112.7
102.5°	1332.3	1302.7	1185.0	973.5	710.6	471.4	307.4	212.5	161.1	146.3	131.5
105°	1375.8	1277.9	1107.0	880.6	648.4	449.7	311.3	229.3	181.9	167.6	153.2
107.5°	1332.3	1195.9	1011.1	804.5	607.8	443.8	323.2	247.1	203.6	189.2	174.9
110°	1240.4	1097.1	926.1	750.2	589.1	445.7	337.0	267.8	224.4	211.0	197.7

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1143.5	1010.1	863.8	719.5	580.2	451.7	351.9	287.6	246.1	232.8	219.4
115°	1063.5	947.8	826.3	702.7	578.2	459.6	367.7	308.4	268.8	255.4	242.1
117.5°	1001.2	907.3	804.5	693.8	577.2	467.5	383.5	328.1	290.6	276.8	262.9
120°	961.7	882.6	790.7	686.9	577.2	476.4	400.3	348.9	311.3	297.5	283.7
122.5°	937.0	866.8	778.8	679.0	576.2	485.3	416.1	368.7	331.1	317.8	304.4
125°	918.2	850.0	765.0	670.1	575.2	494.2	431.9	386.4	350.9	337.0	323.2
127.5°	899.4	831.2	749.2	658.2	573.2	501.1	445.7	403.3	368.7	354.8	341.0
130°	874.7	807.5	729.4	647.4	572.3	509.0	458.6	420.1	386.4	372.1	357.8
132.5°	846.0	780.8	708.7	637.5	571.3	515.9	471.4	433.9	400.3	387.0	373.6
135°	814.4	754.1	689.9	627.6	570.3	522.8	482.3	446.7	414.1	401.2	388.4
137.5°	780.8	728.4	672.1	618.7	570.3	526.8	490.2	456.6	426.0	413.6	401.3
140°	748.2	703.7	657.3	611.8	569.3	531.7	498.1	466.5	436.9	425.0	413.1
142.5°	719.5	683.0	643.4	605.9	569.3	535.7	504.1	475.4	446.7	435.4	424.0
145°	693.8	664.2	630.6	598.9	567.3	536.7	508.0	481.3	455.6	444.8	433.9
147.5°	672.1	647.4	619.7	593.0	564.4	537.7	512.0	488.2	463.5	453.6	443.8
150°	652.3	632.5	609.8	586.1	561.4	537.7	514.9	493.2	471.4	462.0	452.7
152.5°	635.5	617.7	598.9	578.2	556.4	535.7	516.9	497.1	478.4	470.0	461.6
155°	618.7	603.9	588.1	570.3	551.5	533.7	517.9	501.1	484.3	476.9	469.5
157.5°	602.9	590.1	576.2	562.4	546.6	531.7	517.9	504.1	489.2	483.3	477.4
160°	587.1	576.2	565.3	553.5	540.6	528.8	517.9	506.0	494.2	488.8	483.3
162.5°	571.3	563.4	554.5	545.6	534.7	525.8	517.9	508.0	497.1	493.2	489.2
165°	557.4	550.5	544.6	536.7	528.8	521.9	515.9	508.0	499.1	496.2	493.2
167.5°	545.6	539.6	534.7	528.8	522.8	517.9	513.9	508.0	501.1	498.6	496.2
170°	532.7	528.8	525.8	520.9	516.9	513.9	512.0	507.0	502.1	500.6	499.1
172.5°	521.9	519.9	517.9	513.9	511.0	510.0	510.0	506.0	503.1	502.1	501.1
175°	513.9	512.0	511.0	509.0	507.0	507.0	508.0	505.1	503.1	503.1	503.1
177.5°	507.0	507.0	506.0	505.1	504.1	504.1	506.0	504.1	503.1	503.1	503.1
180°	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1	503.1

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	961.7	961.7	961.7	961.7
2.5°	940.0	944.6	952.4	963.2
5°	918.3	931.5	943.9	960.1
7.5°	898.9	914.4	931.5	954.7
10°	876.4	895.8	917.5	946.2
12.5°	850.1	877.2	902.0	933.0
15°	830.7	850.9	882.6	919.1
17.5°	803.6	830.7	862.5	903.6
20°	778.0	806.7	842.3	885.0
22.5°	750.9	783.4	819.1	864.8
25°	723.0	757.9	793.5	842.3
27.5°	697.4	729.2	769.5	819.1
30°	666.4	702.9	741.6	793.5
32.5°	636.2	674.2	713.7	765.6
35°	603.7	641.6	685.0	734.6
37.5°	571.9	613.7	653.3	701.3
40°	537.0	580.4	621.5	670.3
42.5°	502.9	547.9	588.9	630.8
45°	471.2	515.3	552.5	592.0
47.5°	440.9	480.4	518.4	554.1
50°	411.5	444.8	479.7	509.1
52.5°	380.5	412.3	440.2	466.5
55°	352.6	377.4	402.2	426.2
57.5°	319.3	344.1	365.8	384.4
60°	291.4	306.9	327.8	347.2
62.5°	259.6	277.4	293.7	306.1
65°	228.6	244.1	256.5	267.3
67.5°	202.3	211.6	220.9	232.5
70°	170.5	178.2	189.1	197.6
72.5°	143.4	149.6	155.0	165.1
75°	116.2	121.7	124.8	134.1
77.5°	89.9	95.3	97.6	103.1
80°	69.0	69.7	72.8	77.5
82.5°	47.3	48.8	49.6	53.5
85°	27.1	31.0	30.2	31.8
87.5°	11.6	12.4	13.9	15.5
90°	6.9	5.9	3.0	1.0
92.5°	45.5	30.6	19.8	13.8
95°	58.3	45.5	35.6	32.6
97.5°	75.1	63.3	54.4	54.4
100°	93.9	82.0	75.1	75.1
102.5°	113.7	102.8	96.9	94.9
105°	135.4	123.5	118.6	115.6
107.5°	158.1	145.3	140.3	138.4
110°	179.9	168.0	163.1	161.1

TEST NUMBER: P1026387

CATALOG NUMBER: S124RDIP-B575D1035UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	201.6	190.8	184.8	182.8
115°	223.4	213.5	206.6	203.6
117.5°	245.1	234.2	228.3	225.3
120°	266.9	256.0	249.1	247.1
122.5°	285.6	275.8	268.8	266.9
125°	304.4	293.5	287.6	283.7
127.5°	321.2	309.4	302.4	299.5
130°	339.0	324.2	316.3	312.3
132.5°	352.8	339.0	328.1	325.2
135°	367.7	350.9	341.0	337.0
137.5°	379.5	363.7	352.8	348.9
140°	392.4	375.6	364.7	361.7
142.5°	404.2	388.4	378.5	375.6
145°	415.1	401.3	391.4	388.4
147.5°	428.0	413.1	404.2	403.3
150°	437.8	426.0	418.1	417.1
152.5°	448.7	437.8	429.9	429.9
155°	458.6	448.7	442.8	441.8
157.5°	467.5	459.6	453.7	453.7
160°	475.4	468.5	464.5	464.5
162.5°	482.3	476.4	473.4	474.4
165°	488.2	483.3	481.3	481.3
167.5°	493.2	489.2	488.2	489.2
170°	497.1	494.2	493.2	494.2
172.5°	500.1	498.1	498.1	499.1
175°	502.1	501.1	501.1	502.1
177.5°	503.1	502.1	503.1	504.1
180°	503.1	503.1	503.1	503.1

(END OF REPORT)