

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026488

Luminaire Tested: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026488
REPORT IS A COMBINATION OF REPORTS P999568 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D590UB40-4F0-XX-W2A-A1
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4457.0 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	88	92	88	85	82	76	74	71	64	63	61	54	53	52
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	67	61	77	69	63	58	60	55	51	51	47	45	43	40	38
4	76	66	58	52	71	61	55	49	53	48	44	46	42	39	39	36	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	29	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	27	23	21
9	52	40	32	27	48	38	31	26	33	28	24	29	24	21	25	21	19
10	49	37	29	25	45	35	28	24	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7796	7796	7796	7796
5°	7797	8810	7809	6733
10°	7755	10156	7749	5856
15°	7663	11430	7663	4903
20°	7567	12393	7526	4317
25°	7449	12446	7414	3899
30°	7323	10583	7266	3612
35°	7146	7985	7055	3397
40°	6948	5787	6811	3230
45°	6622	4398	6458	3082
50°	6236	3555	6065	2865
55°	5817	2943	5627	2576
60°	5396	2489	5155	2142
65°	4868	2028	4712	1703
70°	4384	1644	4176	1383
75°	3841	1184	3573	1014
80°	3167	786	2883	744
85°	2299	405	1907	405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 9760 cd/sqm

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.6	2.1
10°-20°	279.6	6.3
20°-30°	438.0	9.8
30°-40°	486.3	10.9
40°-50°	431.0	9.7
50°-60°	335.8	7.5
60°-70°	219.7	4.9
70°-80°	107.8	2.4
80°-90°	27.8	0.6
90°-100°	47.9	1.1
100°-110°	143.4	3.2
110°-120°	243.7	5.5
120°-130°	321.3	7.2
130°-140°	360.9	8.1
140°-150°	354.7	8.0
150°-160°	298.4	6.7
160°-170°	198.5	4.5
170°-180°	69.5	1.6
0°-30°	810.1	18.2
0°-40°	1296.5	29.1
0°-60°	2063.3	46.3
0°-90°	2418.6	54.3
90°-120°	435.0	9.8
90°-150°	1472.0	33.0
90°-180°	2038.0	45.7
0°-180°	4457.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	956	956	956	956	956	
5°	955	1105	956	844	955	91
15°	914	1464	914	628	914	258
25°	838	1579	834	495	838	386
35°	730	972	721	414	730	457
45°	589	497	574	348	589	454
55°	424	297	410	260	424	379
65°	266	173	257	146	266	265
75°	133	80	124	69	133	141
85°	32	19	26	19	32	36
90°	2	17	2	17	2	5
95°	34	45	34	45	34	37
105°	132	139	132	139	132	140
115°	248	246	248	246	248	244
125°	361	358	361	358	361	322
135°	465	466	465	466	465	360
145°	565	566	565	566	565	354
155°	648	647	648	647	648	298
165°	705	703	705	703	705	199
175°	734	730	734	730	734	70
180°	735	735	735	735	735	

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1
2.5°	957.7	966.2	970.8	974.6	982.3	985.4	991.6	993.1	999.3	998.5	996.2
5°	954.6	969.2	980.0	991.6	1005.4	1013.1	1021.6	1034.0	1040.1	1048.6	1054.0
7.5°	949.2	969.2	987.0	1004.7	1027.0	1039.3	1050.1	1069.4	1085.6	1099.4	1114.9
10°	940.7	966.2	992.3	1016.2	1047.0	1061.7	1077.9	1106.4	1128.7	1148.0	1172.6
12.5°	927.6	963.1	992.3	1024.7	1064.0	1084.0	1105.6	1139.5	1165.7	1197.3	1228.1
15°	913.8	953.1	991.6	1034.0	1078.6	1101.8	1123.3	1168.8	1208.8	1245.1	1279.0
17.5°	898.4	941.5	983.9	1030.9	1084.8	1113.3	1138.7	1193.4	1237.4	1284.4	1318.3
20°	879.9	926.9	975.4	1027.8	1088.7	1120.2	1148.8	1211.2	1259.7	1310.5	1352.9
22.5°	859.8	910.7	963.8	1020.9	1084.0	1118.7	1151.8	1218.9	1275.1	1322.1	1379.1
25°	837.5	891.4	946.1	1006.2	1077.1	1114.9	1148.8	1215.0	1275.1	1336.7	1392.2
27.5°	814.4	869.8	926.9	990.0	1062.5	1099.4	1138.0	1201.9	1272.0	1339.1	1395.3
30°	788.9	842.9	903.0	963.1	1040.1	1077.1	1116.4	1185.7	1262.0	1329.0	1389.9
32.5°	761.2	816.7	873.7	936.1	1011.6	1051.7	1087.9	1166.5	1244.3	1310.5	1367.6
35°	730.4	782.8	836.7	900.7	975.4	1011.6	1054.8	1136.4	1215.0	1285.1	1322.1
37.5°	697.3	747.3	797.4	860.6	932.3	976.2	1018.5	1101.0	1184.2	1231.2	1250.5
40°	666.4	710.4	754.3	815.1	887.6	933.0	976.2	1061.7	1134.9	1171.1	1156.5
42.5°	627.2	672.6	711.9	768.1	841.3	883.7	927.6	1016.2	1075.6	1090.2	1054.0
45°	588.6	626.4	664.1	718.8	795.9	832.1	879.1	961.5	1010.8	997.7	944.6
47.5°	550.9	581.7	617.1	670.3	739.6	782.8	826.7	898.4	933.0	914.5	840.6
50°	506.2	537.0	574.0	620.2	687.2	728.9	763.5	829.8	856.0	810.5	721.1
52.5°	463.8	490.8	522.4	565.5	629.5	667.2	705.0	762.0	770.5	718.1	624.1
55°	423.8	445.3	478.5	513.1	571.7	611.7	637.9	686.5	684.2	618.7	537.8
57.5°	382.1	402.2	424.5	460.7	516.2	546.3	574.8	617.1	594.8	539.3	459.2
60°	345.2	356.7	379.1	413.7	460.7	486.9	509.3	532.4	513.1	453.0	391.4
62.5°	304.3	317.4	333.6	361.3	402.9	427.6	443.8	453.8	433.8	387.5	331.3
65°	265.8	277.4	294.3	319.0	350.6	369.0	377.5	384.5	373.7	321.3	276.6
67.5°	231.1	238.8	254.3	270.4	304.3	309.0	320.5	323.6	302.0	262.0	226.5
70°	196.5	204.2	211.1	230.4	245.8	254.3	256.6	256.6	235.0	208.8	179.5
72.5°	164.1	168.7	175.7	188.8	197.2	203.4	206.5	202.6	182.6	161.0	139.5
75°	133.3	135.6	141.8	150.2	157.2	154.9	154.1	149.5	134.8	119.4	107.1
77.5°	102.5	104.0	110.9	113.3	113.3	115.6	112.5	107.9	95.5	84.0	78.6
80°	77.0	79.4	80.1	81.7	80.1	80.1	77.8	70.1	63.9	58.6	54.7
82.5°	53.2	54.7	55.5	53.2	54.7	52.4	48.5	43.1	39.3	38.5	37.0
85°	31.6	32.4	31.6	31.6	29.3	28.5	25.4	24.7	23.1	23.1	22.3
87.5°	15.4	14.6	13.1	11.6	11.6	10.8	11.6	10.0	11.6	10.8	10.0
90°	1.7	3.1	4.5	5.9	7.3	8.0	8.5	9.5	10.5	11.5	12.5
92.5°	14.8	16.4	18.1	19.7	21.4	22.2	22.5	23.1	23.8	24.4	25.0
95°	34.1	35.2	36.4	37.5	38.6	39.2	39.6	40.5	41.4	42.3	43.2
97.5°	54.5	55.5	56.5	57.6	58.6	59.1	59.6	60.6	61.6	62.6	63.6
100°	79.5	80.0	80.5	81.0	81.5	81.8	82.4	83.5	84.6	85.8	86.9
102.5°	105.7	105.8	106.0	106.1	106.2	106.3	106.8	107.8	108.8	109.8	110.8
105°	132.4	132.5	132.7	132.8	132.9	133.0	133.2	133.7	134.2	134.7	135.2
107.5°	160.2	160.3	160.5	160.6	160.7	160.8	160.9	161.0	161.1	161.3	161.4
110°	188.6	188.9	189.1	189.4	189.7	189.8	189.7	189.6	189.5	189.3	189.2

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	218.2	218.2	218.2	218.2	218.2	218.2	218.1	217.8	217.5	217.3	217.0
115°	247.7	247.7	247.7	247.7	247.7	247.7	247.6	247.3	247.1	246.8	246.6
117.5°	275.6	275.6	275.6	275.6	275.6	275.6	275.5	275.4	275.3	275.1	275.0
120°	303.4	303.9	304.4	304.9	305.4	305.7	305.5	305.1	304.8	304.4	304.0
122.5°	332.4	332.5	332.7	332.8	332.9	333.0	332.9	332.8	332.7	332.5	332.4
125°	360.8	360.8	360.8	360.8	360.8	360.8	360.7	360.6	360.5	360.3	360.2
127.5°	386.4	386.8	387.2	387.5	387.9	388.1	388.0	387.7	387.4	387.2	386.9
130°	413.6	414.0	414.4	414.7	415.1	415.3	415.3	415.3	415.3	415.3	415.3
132.5°	441.5	441.7	442.0	442.2	442.5	442.6	442.5	442.4	442.3	442.1	442.0
135°	465.3	466.1	466.9	467.6	468.4	468.8	468.8	468.8	468.8	468.8	468.8
137.5°	492.1	492.5	492.9	493.2	493.6	493.8	493.9	494.2	494.4	494.7	494.9
140°	518.8	519.0	519.3	519.5	519.8	519.9	519.9	519.9	519.9	519.9	519.9
142.5°	543.2	543.4	543.7	543.9	544.2	544.3	544.2	544.1	544.0	543.9	543.8
145°	565.3	565.8	566.3	566.8	567.3	567.6	567.7	567.8	567.9	568.1	568.2
147.5°	588.1	588.7	589.3	590.0	590.6	590.9	590.8	590.7	590.6	590.4	590.3
150°	608.5	609.0	609.5	610.0	610.5	610.8	610.8	610.8	610.8	610.8	610.8
152.5°	627.8	628.1	628.3	628.6	628.9	629.0	629.1	629.2	629.3	629.5	629.6
155°	647.7	647.7	647.7	647.7	647.7	647.7	647.6	647.5	647.4	647.3	647.2
157.5°	664.8	664.5	664.3	664.0	663.7	663.6	663.6	663.6	663.6	663.6	663.6
160°	679.6	679.5	679.3	679.2	679.1	679.0	678.9	678.8	678.7	678.5	678.4
162.5°	693.2	692.8	692.4	692.1	691.7	691.5	691.4	691.3	691.2	691.0	690.9
165°	705.1	704.7	704.3	704.0	703.6	703.4	703.3	703.0	702.8	702.5	702.3
167.5°	714.8	714.3	713.8	713.3	712.8	712.5	712.5	712.5	712.5	712.5	712.5
170°	722.7	722.1	721.5	720.8	720.2	719.9	720.0	720.1	720.2	720.4	720.5
172.5°	728.4	727.9	727.4	726.9	726.4	726.1	726.1	726.1	726.1	726.1	726.1
175°	733.5	732.9	732.3	731.6	731.0	730.7	730.6	730.5	730.4	730.2	730.1
177.5°	735.8	735.2	734.6	733.9	733.3	733.0	733.0	733.0	733.0	733.0	733.0
180°	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1
2.5°	1002.4	1010.8	1011.6	1019.3	1017.0	1013.1	1020.1	1015.5	1024.7	1021.6	1025.5
5°	1060.9	1072.5	1082.5	1088.7	1099.4	1097.1	1108.7	1104.8	1113.3	1104.8	1115.6
7.5°	1129.5	1148.8	1158.8	1174.9	1179.6	1180.3	1194.2	1197.3	1202.7	1197.3	1203.5
10°	1196.5	1219.6	1242.7	1255.8	1264.3	1275.9	1288.2	1293.6	1297.4	1292.1	1295.9
12.5°	1257.4	1293.6	1319.0	1345.2	1351.4	1361.4	1374.5	1373.0	1388.4	1385.3	1392.2
15°	1313.6	1353.7	1384.5	1405.3	1422.3	1430.7	1455.4	1456.9	1456.2	1463.9	1459.2
17.5°	1363.7	1397.6	1441.5	1468.5	1489.3	1489.3	1503.2	1531.7	1529.4	1528.6	1533.2
20°	1404.5	1443.1	1483.9	1529.4	1546.3	1549.4	1568.6	1583.3	1585.6	1585.6	1585.6
22.5°	1435.4	1480.8	1524.7	1557.1	1570.2	1581.0	1597.9	1607.2	1610.3	1608.7	1610.3
25°	1450.8	1493.9	1538.6	1567.9	1575.6	1581.7	1583.3	1588.7	1587.9	1578.7	1584.1
27.5°	1453.9	1495.5	1524.7	1532.4	1528.6	1524.7	1500.1	1502.4	1495.5	1481.6	1487.0
30°	1440.0	1462.3	1461.6	1437.7	1430.7	1414.6	1392.2	1359.1	1332.1	1320.6	1324.4
32.5°	1389.9	1389.9	1362.2	1308.2	1284.4	1255.1	1215.0	1185.0	1149.5	1141.8	1156.5
35°	1320.6	1281.3	1230.4	1159.5	1123.3	1101.8	1032.4	1010.8	980.8	972.3	979.2
37.5°	1212.7	1147.2	1073.2	1007.0	976.2	937.6	876.8	846.0	824.4	809.7	816.7
40°	1091.7	1012.4	935.3	853.7	819.8	788.2	742.7	715.0	680.3	681.9	684.2
42.5°	976.2	882.9	796.7	721.1	688.8	662.6	631.0	597.1	584.8	580.9	577.1
45°	853.7	754.3	673.4	617.1	587.9	563.2	533.9	514.7	500.0	496.9	500.8
47.5°	738.1	654.1	577.1	524.7	500.8	488.5	465.4	447.6	438.4	430.7	435.3
50°	633.3	554.7	493.1	449.2	432.2	423.8	402.2	392.9	383.7	381.4	380.6
52.5°	547.0	480.0	426.8	391.4	378.3	373.7	357.5	344.4	336.7	339.0	340.5
55°	468.4	411.4	369.8	341.3	330.5	325.1	313.6	304.3	298.9	296.6	298.2
57.5°	399.1	349.8	319.7	296.6	288.2	285.8	273.5	270.4	266.6	264.3	264.3
60°	335.9	301.2	273.5	260.4	251.2	248.9	239.6	235.8	235.0	232.7	231.1
62.5°	282.8	254.3	235.0	221.1	217.3	216.5	210.3	205.7	203.4	201.9	201.9
65°	236.5	215.7	199.5	189.5	186.5	184.9	178.0	176.4	174.9	173.4	172.6
67.5°	197.2	178.7	167.2	160.3	156.4	157.2	153.3	150.2	150.2	149.5	148.7
70°	159.5	147.9	137.9	134.1	132.5	131.0	129.4	127.1	126.4	126.4	126.4
72.5°	125.6	117.9	112.5	110.2	108.6	107.1	105.6	105.6	105.6	104.8	104.8
75°	96.3	93.2	89.4	87.1	87.1	88.6	86.3	84.0	81.7	80.1	80.9
77.5°	72.4	70.9	68.6	64.7	65.5	63.9	63.9	62.4	63.2	63.2	61.6
80°	53.2	50.9	50.1	47.8	48.5	47.8	47.0	47.0	45.5	45.5	45.5
82.5°	37.0	34.7	34.7	33.9	33.1	33.1	32.4	32.4	33.1	31.6	31.6
85°	22.3	21.6	21.6	20.0	20.0	20.0	20.0	20.8	20.0	19.3	19.3
87.5°	10.0	10.8	10.0	9.2	9.2	9.2	8.5	8.5	7.7	8.5	8.5
90°	13.3	14.0	14.8	15.5	15.9	16.0	16.3	16.5	16.8	17.0	16.8
92.5°	25.4	25.8	26.1	26.5	26.7	26.8	26.9	27.0	27.2	27.3	27.2
95°	43.6	44.0	44.3	44.7	44.9	44.9	44.9	44.9	44.9	44.9	44.9
97.5°	64.1	64.6	65.1	65.6	65.9	65.9	65.9	65.9	65.9	65.9	65.9
100°	87.2	87.4	87.7	88.0	88.1	88.1	88.1	88.1	88.1	88.1	88.1
102.5°	111.2	111.6	111.9	112.3	112.5	112.6	112.7	112.8	113.0	113.1	113.0
105°	135.6	136.0	136.3	136.7	136.9	137.1	137.5	137.8	138.2	138.6	138.2
107.5°	161.9	162.4	162.9	163.4	163.6	163.5	163.4	163.3	163.2	163.1	163.2
110°	189.0	188.7	188.5	188.2	188.1	188.3	188.7	189.0	189.4	189.8	189.4

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0
115°	246.5	246.3	246.2	246.1	246.0	245.9	245.8	245.7	245.6	245.5	245.6
117.5°	274.6	274.2	273.9	273.5	273.3	273.1	272.7	272.4	272.0	271.6	272.0
120°	303.4	302.7	302.1	301.4	301.1	301.2	301.5	301.8	302.0	302.3	302.0
122.5°	332.0	331.6	331.3	330.9	330.7	330.4	329.7	329.1	328.4	327.8	328.4
125°	360.0	359.7	359.5	359.2	359.1	359.0	358.7	358.5	358.2	358.0	358.2
127.5°	386.7	386.4	386.2	385.9	385.8	385.7	385.6	385.5	385.3	385.2	385.3
130°	415.1	414.8	414.6	414.3	414.2	413.9	413.4	412.9	412.4	411.9	412.4
132.5°	441.8	441.5	441.3	441.0	440.9	440.8	440.7	440.6	440.4	440.3	440.4
135°	468.5	468.3	468.0	467.7	467.6	467.4	467.0	466.7	466.3	465.9	466.3
137.5°	494.5	494.1	493.8	493.4	493.2	493.3	493.4	493.5	493.7	493.8	493.7
140°	519.8	519.6	519.5	519.4	519.3	519.2	519.1	519.0	518.9	518.8	518.9
142.5°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8
145°	568.1	567.9	567.8	567.7	567.6	567.4	567.0	566.7	566.3	565.9	566.3
147.5°	590.2	590.1	590.0	589.9	589.8	589.7	589.6	589.5	589.3	589.2	589.3
150°	610.8	610.8	610.8	610.8	610.8	610.7	610.6	610.5	610.3	610.2	610.3
152.5°	630.0	630.4	630.7	631.1	631.3	631.1	630.7	630.4	630.0	629.6	630.0
155°	647.7	648.2	648.7	649.2	649.4	649.2	648.7	648.2	647.7	647.2	647.7
157.5°	664.0	664.4	664.7	665.1	665.3	665.1	664.7	664.4	664.0	663.6	664.0
160°	678.8	679.2	679.5	679.9	680.1	679.8	679.2	678.5	677.9	677.3	677.9
162.5°	691.7	692.4	693.2	693.9	694.3	694.0	693.4	692.7	692.1	691.5	692.1
165°	703.1	703.8	704.6	705.3	705.7	705.4	704.9	704.4	703.9	703.4	703.9
167.5°	713.3	714.0	714.8	715.5	715.9	715.5	714.8	714.0	713.3	712.5	713.3
170°	721.3	722.0	722.8	723.5	723.9	723.5	722.6	721.7	720.8	719.9	720.8
172.5°	727.0	727.9	728.8	729.7	730.1	729.7	728.8	727.9	727.0	726.1	727.0
175°	731.0	731.9	732.8	733.7	734.1	733.7	732.8	731.9	731.0	730.1	731.0
177.5°	733.9	734.7	735.6	736.5	736.9	736.4	735.4	734.4	733.4	732.4	733.4
180°	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1
2.5°	1027.8	1022.4	1021.6	1021.6	1013.1	1017.8	1008.5	998.5	993.9	993.9	985.4
5°	1113.3	1107.9	1102.5	1094.0	1094.0	1089.4	1074.8	1060.1	1049.4	1040.1	1030.1
7.5°	1201.1	1195.7	1180.3	1171.9	1176.5	1167.2	1148.0	1123.3	1104.8	1090.2	1069.4
10°	1296.7	1282.0	1274.3	1269.7	1253.5	1243.5	1221.2	1185.0	1161.8	1142.6	1115.6
12.5°	1374.5	1379.1	1349.8	1352.2	1336.0	1322.1	1287.4	1252.8	1218.1	1191.1	1151.1
15°	1458.5	1444.6	1426.9	1413.0	1407.6	1390.7	1361.4	1315.2	1277.4	1235.0	1189.6
17.5°	1524.7	1513.9	1497.0	1483.9	1472.3	1431.5	1406.9	1366.0	1314.4	1272.8	1217.3
20°	1581.0	1571.0	1547.1	1538.6	1517.8	1488.5	1453.1	1389.9	1343.7	1298.2	1244.3
22.5°	1604.9	1594.8	1574.0	1563.3	1550.2	1521.7	1487.8	1427.7	1370.6	1313.6	1256.6
25°	1584.8	1584.8	1574.8	1571.0	1559.4	1534.0	1499.3	1448.5	1387.6	1326.0	1258.2
27.5°	1487.8	1507.0	1513.9	1517.8	1517.8	1518.6	1494.7	1445.4	1386.1	1326.0	1255.1
30°	1347.5	1379.9	1408.4	1416.9	1431.5	1447.7	1457.7	1433.8	1380.7	1317.5	1246.6
32.5°	1171.1	1212.7	1265.9	1279.0	1299.0	1347.5	1374.5	1384.5	1355.2	1299.8	1224.3
35°	995.4	1047.8	1080.2	1120.2	1138.7	1210.4	1270.5	1306.7	1299.8	1266.6	1198.1
37.5°	842.1	872.2	911.4	953.8	990.8	1059.4	1134.1	1204.2	1232.7	1216.6	1164.9
40°	695.0	730.4	777.4	812.1	837.5	906.1	998.5	1074.8	1137.2	1147.2	1115.6
42.5°	590.9	626.4	654.9	692.6	712.7	778.9	860.6	956.1	1030.1	1069.4	1055.5
45°	510.8	532.4	555.5	577.1	601.7	660.3	735.8	840.6	923.8	979.2	984.6
47.5°	440.7	460.0	480.0	500.0	513.9	559.4	628.7	714.2	805.1	881.4	911.4
50°	391.4	400.6	415.3	426.8	443.0	482.3	537.8	611.7	708.0	790.5	829.8
52.5°	342.9	354.4	366.0	376.0	386.8	414.5	465.4	529.3	612.5	697.3	745.8
55°	302.0	311.3	322.1	329.0	335.1	359.8	398.3	447.6	519.3	599.4	659.5
57.5°	268.9	272.7	282.0	285.8	292.8	312.8	340.5	384.5	442.2	520.1	569.4
60°	232.7	240.4	247.3	250.4	255.8	269.7	288.9	329.8	379.8	436.8	493.1
62.5°	203.4	206.5	211.9	215.7	219.6	234.2	250.4	281.2	319.0	366.7	418.4
65°	176.4	178.0	181.1	186.5	188.8	199.5	208.8	231.1	266.6	302.8	354.4
67.5°	148.7	150.2	154.1	157.2	159.5	166.4	176.4	192.6	211.9	251.9	280.4
70°	127.1	127.1	129.4	131.0	133.3	136.4	141.8	154.1	171.8	197.2	223.4
72.5°	106.3	106.3	106.3	108.6	108.6	110.9	114.0	122.5	134.8	154.9	171.8
75°	82.4	83.2	84.8	84.8	85.5	88.6	90.9	93.2	99.4	112.5	127.9
77.5°	62.4	63.9	64.7	63.2	64.7	64.7	67.8	70.9	74.0	77.8	89.4
80°	46.2	47.0	45.5	46.2	46.2	47.8	49.3	48.5	50.1	54.7	57.8
82.5°	30.8	31.6	31.6	31.6	31.6	33.9	33.9	33.1	33.9	34.7	35.4
85°	19.3	18.5	18.5	19.3	18.5	18.5	19.3	20.0	19.3	20.0	20.8
87.5°	8.5	8.5	8.5	8.5	7.7	7.7	8.5	7.7	8.5	7.7	6.9
90°	16.5	16.3	16.0	15.9	15.5	14.8	14.0	13.3	12.5	11.5	10.5
92.5°	27.0	26.9	26.8	26.7	26.5	26.1	25.8	25.4	25.0	24.4	23.8
95°	44.9	44.9	44.9	44.9	44.7	44.3	44.0	43.6	43.2	42.3	41.4
97.5°	65.9	65.9	65.9	65.9	65.6	65.1	64.6	64.1	63.6	62.6	61.6
100°	88.1	88.1	88.1	88.1	88.0	87.7	87.4	87.2	86.9	85.8	84.6
102.5°	112.8	112.7	112.6	112.5	112.3	111.9	111.6	111.2	110.8	109.8	108.8
105°	137.8	137.5	137.1	136.9	136.7	136.3	136.0	135.6	135.2	134.7	134.2
107.5°	163.3	163.4	163.5	163.6	163.4	162.9	162.4	161.9	161.4	161.3	161.1
110°	189.0	188.7	188.3	188.1	188.2	188.5	188.7	189.0	189.2	189.3	189.5

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.3	217.5
115°	245.7	245.8	245.9	246.0	246.1	246.2	246.3	246.5	246.6	246.8	247.1
117.5°	272.4	272.7	273.1	273.3	273.5	273.9	274.2	274.6	275.0	275.1	275.3
120°	301.8	301.5	301.2	301.1	301.4	302.1	302.7	303.4	304.0	304.4	304.8
122.5°	329.1	329.7	330.4	330.7	330.9	331.3	331.6	332.0	332.4	332.5	332.7
125°	358.5	358.7	359.0	359.1	359.2	359.5	359.7	360.0	360.2	360.3	360.5
127.5°	385.5	385.6	385.7	385.8	385.9	386.2	386.4	386.7	386.9	387.2	387.4
130°	412.9	413.4	413.9	414.2	414.3	414.6	414.8	415.1	415.3	415.3	415.3
132.5°	440.6	440.7	440.8	440.9	441.0	441.3	441.5	441.8	442.0	442.1	442.3
135°	466.7	467.0	467.4	467.6	467.7	468.0	468.3	468.5	468.8	468.8	468.8
137.5°	493.5	493.4	493.3	493.2	493.4	493.8	494.1	494.5	494.9	494.7	494.4
140°	519.0	519.1	519.2	519.3	519.4	519.5	519.6	519.8	519.9	519.9	519.9
142.5°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.9	544.0
145°	566.7	567.0	567.4	567.6	567.7	567.8	567.9	568.1	568.2	568.1	567.9
147.5°	589.5	589.6	589.7	589.8	589.9	590.0	590.1	590.2	590.3	590.4	590.6
150°	610.5	610.6	610.7	610.8	610.8	610.8	610.8	610.8	610.8	610.8	610.8
152.5°	630.4	630.7	631.1	631.3	631.1	630.7	630.4	630.0	629.6	629.5	629.3
155°	648.2	648.7	649.2	649.4	649.2	648.7	648.2	647.7	647.2	647.3	647.4
157.5°	664.4	664.7	665.1	665.3	665.1	664.7	664.4	664.0	663.6	663.6	663.6
160°	678.5	679.2	679.8	680.1	679.9	679.5	679.2	678.8	678.4	678.5	678.7
162.5°	692.7	693.4	694.0	694.3	693.9	693.2	692.4	691.7	690.9	691.0	691.2
165°	704.4	704.9	705.4	705.7	705.3	704.6	703.8	703.1	702.3	702.5	702.8
167.5°	714.0	714.8	715.5	715.9	715.5	714.8	714.0	713.3	712.5	712.5	712.5
170°	721.7	722.6	723.5	723.9	723.5	722.8	722.0	721.3	720.5	720.4	720.2
172.5°	727.9	728.8	729.7	730.1	729.7	728.8	727.9	727.0	726.1	726.1	726.1
175°	731.9	732.8	733.7	734.1	733.7	732.8	731.9	731.0	730.1	730.2	730.4
177.5°	734.4	735.4	736.4	736.9	736.5	735.6	734.7	733.9	733.0	733.0	733.0
180°	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1
2.5°	980.8	976.9	974.6	973.9	966.9	963.1	960.8	959.2	956.9	950.7	945.3
5°	1017.8	1007.0	1001.6	995.4	984.6	972.3	962.3	956.1	948.4	936.1	924.5
7.5°	1052.4	1036.3	1025.5	1017.0	998.5	978.5	962.3	949.2	934.6	917.6	901.4
10°	1088.7	1062.5	1048.6	1035.5	1008.5	982.3	959.2	940.0	919.2	896.8	879.1
12.5°	1117.2	1082.5	1067.1	1048.6	1015.5	984.6	955.4	929.2	902.2	878.3	852.9
15°	1150.3	1107.1	1089.4	1065.5	1020.1	980.0	942.3	913.8	886.0	850.6	823.6
17.5°	1169.6	1119.5	1094.0	1073.2	1023.9	975.4	931.5	896.0	863.7	828.2	799.7
20°	1188.8	1131.8	1103.3	1074.0	1015.5	963.8	917.6	875.2	841.3	802.8	773.5
22.5°	1195.0	1128.7	1098.7	1071.7	1010.1	952.3	899.1	856.0	816.7	778.2	745.0
25°	1195.0	1127.9	1092.5	1057.8	993.1	933.8	880.6	833.6	789.7	751.2	718.1
27.5°	1182.7	1112.5	1075.6	1044.0	976.9	913.0	858.3	806.7	764.3	725.8	688.0
30°	1167.2	1090.2	1053.2	1015.5	950.7	889.9	830.6	782.8	738.1	694.2	660.3
32.5°	1148.0	1066.3	1025.5	987.0	918.4	855.2	800.5	753.5	711.1	665.7	627.9
35°	1120.2	1030.9	985.4	951.5	885.3	819.8	767.4	721.1	680.3	633.3	592.5
37.5°	1084.8	998.5	952.3	910.7	842.1	782.0	732.7	688.0	648.0	604.8	559.4
40°	1043.2	953.1	913.0	869.1	796.7	739.6	693.4	653.3	613.3	572.4	528.5
42.5°	996.2	906.8	862.1	819.8	750.4	694.2	651.0	614.8	577.8	540.1	493.1
45°	940.0	856.0	812.8	772.8	705.7	648.0	608.7	574.0	542.4	503.9	462.3
47.5°	876.8	803.6	759.7	716.5	651.0	601.0	562.4	533.2	506.2	467.7	429.9
50°	815.1	742.7	707.3	663.4	603.3	556.3	517.0	492.3	471.5	433.8	399.9
52.5°	737.3	682.6	648.7	611.0	553.2	505.4	474.6	453.0	428.4	399.1	369.0
55°	668.8	617.9	590.9	555.5	498.5	456.1	429.9	409.9	390.6	364.4	340.5
57.5°	590.9	559.4	532.4	501.6	445.3	409.1	386.0	369.0	351.3	329.8	310.5
60°	509.3	494.6	468.4	443.8	396.0	364.4	345.2	329.8	312.8	295.1	278.9
62.5°	436.8	428.4	413.0	393.7	349.0	322.1	302.8	291.2	278.9	262.7	247.3
65°	368.3	364.4	349.8	335.9	305.1	281.2	264.3	257.3	243.5	231.1	217.3
67.5°	307.4	302.8	294.3	288.2	262.0	239.6	231.1	221.9	210.3	201.1	189.5
70°	245.8	245.0	239.6	231.9	218.0	201.9	193.4	187.2	175.7	168.7	160.3
72.5°	191.1	194.9	190.3	187.2	178.0	166.4	158.7	154.9	145.6	140.2	134.1
75°	142.5	145.6	147.9	142.5	140.2	134.8	127.9	124.0	119.4	111.7	109.4
77.5°	97.1	104.0	104.0	105.6	106.3	103.2	97.8	94.8	89.4	87.8	84.8
80°	63.9	70.1	70.9	72.4	74.7	74.7	70.9	70.1	64.7	63.9	61.6
82.5°	37.0	42.4	45.5	47.8	47.0	50.1	47.0	46.2	43.1	43.1	41.6
85°	20.0	20.8	22.3	23.9	25.4	27.0	27.0	26.2	25.4	24.7	23.1
87.5°	7.7	7.7	8.5	7.7	8.5	10.0	10.8	10.8	10.0	9.2	7.7
90°	9.5	8.5	8.0	7.3	5.9	4.5	3.1	1.7	3.1	4.5	5.9
92.5°	23.1	22.5	22.2	21.4	19.7	18.1	16.4	14.8	16.4	18.1	19.7
95°	40.5	39.6	39.2	38.6	37.5	36.4	35.2	34.1	35.2	36.4	37.5
97.5°	60.6	59.6	59.1	58.6	57.6	56.5	55.5	54.5	55.5	56.5	57.6
100°	83.5	82.4	81.8	81.5	81.0	80.5	80.0	79.5	80.0	80.5	81.0
102.5°	107.8	106.8	106.3	106.2	106.1	106.0	105.8	105.7	105.8	106.0	106.1
105°	133.7	133.2	133.0	132.9	132.8	132.7	132.5	132.4	132.5	132.7	132.8
107.5°	161.0	160.9	160.8	160.7	160.6	160.5	160.3	160.2	160.3	160.5	160.6
110°	189.6	189.7	189.8	189.7	189.4	189.1	188.9	188.6	188.9	189.1	189.4

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	217.8	218.1	218.2	218.2	218.2	218.2	218.2	218.2	218.2	218.2	218.2
115°	247.3	247.6	247.7	247.7	247.7	247.7	247.7	247.7	247.7	247.7	247.7
117.5°	275.4	275.5	275.6	275.6	275.6	275.6	275.6	275.6	275.6	275.6	275.6
120°	305.1	305.5	305.7	305.4	304.9	304.4	303.9	303.4	303.9	304.4	304.9
122.5°	332.8	332.9	333.0	332.9	332.8	332.7	332.5	332.4	332.5	332.7	332.8
125°	360.6	360.7	360.8	360.8	360.8	360.8	360.8	360.8	360.8	360.8	360.8
127.5°	387.7	388.0	388.1	387.9	387.5	387.2	386.8	386.4	386.8	387.2	387.5
130°	415.3	415.3	415.3	415.1	414.7	414.4	414.0	413.6	414.0	414.4	414.7
132.5°	442.4	442.5	442.6	442.5	442.2	442.0	441.7	441.5	441.7	442.0	442.2
135°	468.8	468.8	468.8	468.4	467.6	466.9	466.1	465.3	466.1	466.9	467.6
137.5°	494.2	493.9	493.8	493.6	493.2	492.9	492.5	492.1	492.5	492.9	493.2
140°	519.9	519.9	519.9	519.8	519.5	519.3	519.0	518.8	519.0	519.3	519.5
142.5°	544.1	544.2	544.3	544.2	543.9	543.7	543.4	543.2	543.4	543.7	543.9
145°	567.8	567.7	567.6	567.3	566.8	566.3	565.8	565.3	565.8	566.3	566.8
147.5°	590.7	590.8	590.9	590.6	590.0	589.3	588.7	588.1	588.7	589.3	590.0
150°	610.8	610.8	610.8	610.5	610.0	609.5	609.0	608.5	609.0	609.5	610.0
152.5°	629.2	629.1	629.0	628.9	628.6	628.3	628.1	627.8	628.1	628.3	628.6
155°	647.5	647.6	647.7	647.7	647.7	647.7	647.7	647.7	647.7	647.7	647.7
157.5°	663.6	663.6	663.6	663.7	664.0	664.3	664.5	664.8	664.5	664.3	664.0
160°	678.8	678.9	679.0	679.1	679.2	679.3	679.5	679.6	679.5	679.3	679.2
162.5°	691.3	691.4	691.5	691.7	692.1	692.4	692.8	693.2	692.8	692.4	692.1
165°	703.0	703.3	703.4	703.6	704.0	704.3	704.7	705.1	704.7	704.3	704.0
167.5°	712.5	712.5	712.5	712.8	713.3	713.8	714.3	714.8	714.3	713.8	713.3
170°	720.1	720.0	719.9	720.2	720.8	721.5	722.1	722.7	722.1	721.5	720.8
172.5°	726.1	726.1	726.1	726.4	726.9	727.4	727.9	728.4	727.9	727.4	726.9
175°	730.5	730.6	730.7	731.0	731.6	732.3	732.9	733.5	732.9	732.3	731.6
177.5°	733.0	733.0	733.0	733.3	733.9	734.6	735.2	735.8	735.2	734.6	733.9
180°	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1
2.5°	940.7	939.2	937.6	931.5	926.1	916.8	909.1	906.1	905.3	906.1	903.7
5°	913.8	913.0	907.6	896.8	886.8	876.0	868.3	860.6	856.0	856.0	850.6
7.5°	888.3	882.9	878.3	864.5	852.9	838.3	826.7	819.8	815.9	807.4	807.4
10°	861.4	853.7	847.5	834.4	817.5	802.8	788.2	779.7	772.8	766.6	764.3
12.5°	834.4	828.2	816.7	802.8	785.9	767.4	752.0	745.8	729.6	716.5	717.3
15°	809.0	795.1	789.7	769.7	749.7	731.9	709.6	691.9	678.8	670.3	659.5
17.5°	780.5	766.6	756.6	739.6	713.4	685.7	664.1	640.2	627.2	612.5	605.6
20°	748.9	737.3	729.6	702.7	671.1	637.9	614.1	599.4	584.8	574.0	567.8
22.5°	721.9	707.3	698.0	661.8	627.2	594.0	575.5	563.2	550.9	541.6	538.5
25°	687.2	678.8	656.4	624.8	582.5	560.1	543.9	527.8	520.8	514.7	507.7
27.5°	658.7	637.9	622.5	580.9	554.7	529.3	513.1	500.8	492.3	486.2	480.8
30°	623.3	604.0	582.5	547.8	523.9	500.0	485.4	475.4	466.1	462.3	457.7
32.5°	586.3	568.6	547.8	520.1	490.8	472.3	460.7	449.9	443.8	439.9	434.5
35°	553.2	530.8	517.0	490.8	466.9	446.1	435.3	426.1	419.1	417.6	416.8
37.5°	517.7	500.8	487.7	460.7	440.7	423.0	413.0	402.9	399.1	398.3	395.2
40°	486.9	472.3	460.0	434.5	413.0	396.8	389.1	382.9	379.1	379.1	378.3
42.5°	460.0	444.6	432.2	409.1	389.9	375.2	366.7	360.6	359.0	359.8	359.0
45°	429.9	416.8	404.5	380.6	364.4	353.6	344.4	341.3	339.0	339.8	340.5
47.5°	401.4	390.6	378.3	359.0	340.5	329.0	323.6	320.5	320.5	320.5	322.1
50°	376.0	363.7	352.9	332.8	315.9	306.6	302.0	298.2	298.9	299.7	300.5
52.5°	345.9	335.1	327.4	307.4	295.1	283.5	278.1	278.9	278.1	278.1	279.7
55°	319.7	309.0	301.2	282.8	270.4	262.7	258.1	255.8	256.6	255.0	258.1
57.5°	290.5	281.2	275.8	258.1	247.3	240.4	236.5	232.7	234.2	233.4	232.7
60°	265.0	254.3	245.8	233.4	224.2	215.7	213.4	209.6	211.1	209.6	208.8
62.5°	235.8	227.3	221.1	208.8	201.1	194.2	188.8	186.5	185.7	183.4	181.1
65°	206.5	201.9	195.7	183.4	175.7	170.3	167.2	164.9	164.1	157.9	151.0
67.5°	179.5	176.4	170.3	161.0	154.1	148.7	144.1	140.2	135.6	131.0	127.1
70°	154.1	149.5	145.6	137.1	131.0	125.6	121.0	116.3	114.0	109.4	107.9
72.5°	129.4	124.8	121.0	113.3	107.9	102.5	100.9	95.5	93.2	92.5	92.5
75°	104.0	100.2	97.8	90.9	86.3	82.4	80.1	78.6	77.0	75.5	73.2
77.5°	79.4	77.0	75.5	70.9	67.0	64.7	63.9	58.6	57.0	55.5	53.9
80°	57.8	57.0	55.5	51.6	50.1	44.7	44.7	43.1	42.4	42.4	42.4
82.5°	39.3	37.8	37.0	33.1	32.4	31.6	30.8	30.0	30.8	30.0	30.8
85°	20.8	20.0	19.3	19.3	19.3	19.3	19.3	19.3	19.3	18.5	19.3
87.5°	7.7	7.7	7.7	7.7	6.9	7.7	7.7	6.9	7.7	7.7	7.7
90°	7.3	8.0	8.5	9.5	10.5	11.5	12.5	13.3	14.0	14.8	15.5
92.5°	21.4	22.2	22.5	23.1	23.8	24.4	25.0	25.4	25.8	26.1	26.5
95°	38.6	39.2	39.6	40.5	41.4	42.3	43.2	43.6	44.0	44.3	44.7
97.5°	58.6	59.1	59.6	60.6	61.6	62.6	63.6	64.1	64.6	65.1	65.6
100°	81.5	81.8	82.4	83.5	84.6	85.8	86.9	87.2	87.4	87.7	88.0
102.5°	106.2	106.3	106.8	107.8	108.8	109.8	110.8	111.2	111.6	111.9	112.3
105°	132.9	133.0	133.2	133.7	134.2	134.7	135.2	135.6	136.0	136.3	136.7
107.5°	160.7	160.8	160.9	161.0	161.1	161.3	161.4	161.9	162.4	162.9	163.4
110°	189.7	189.8	189.7	189.6	189.5	189.3	189.2	189.0	188.7	188.5	188.2

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	218.2	218.2	218.1	217.8	217.5	217.3	217.0	217.0	217.0	217.0	217.0
115°	247.7	247.7	247.6	247.3	247.1	246.8	246.6	246.5	246.3	246.2	246.1
117.5°	275.6	275.6	275.5	275.4	275.3	275.1	275.0	274.6	274.2	273.9	273.5
120°	305.4	305.7	305.5	305.1	304.8	304.4	304.0	303.4	302.7	302.1	301.4
122.5°	332.9	333.0	332.9	332.8	332.7	332.5	332.4	332.0	331.6	331.3	330.9
125°	360.8	360.8	360.7	360.6	360.5	360.3	360.2	360.0	359.7	359.5	359.2
127.5°	387.9	388.1	388.0	387.7	387.4	387.2	386.9	386.7	386.4	386.2	385.9
130°	415.1	415.3	415.3	415.3	415.3	415.3	415.3	415.1	414.8	414.6	414.3
132.5°	442.5	442.6	442.5	442.4	442.3	442.1	442.0	441.8	441.5	441.3	441.0
135°	468.4	468.8	468.8	468.8	468.8	468.8	468.8	468.5	468.3	468.0	467.7
137.5°	493.6	493.8	493.9	494.2	494.4	494.7	494.9	494.5	494.1	493.8	493.4
140°	519.8	519.9	519.9	519.9	519.9	519.9	519.9	519.8	519.6	519.5	519.4
142.5°	544.2	544.3	544.2	544.1	544.0	543.9	543.8	543.8	543.8	543.8	543.8
145°	567.3	567.6	567.7	567.8	567.9	568.1	568.2	568.1	567.9	567.8	567.7
147.5°	590.6	590.9	590.8	590.7	590.6	590.4	590.3	590.2	590.1	590.0	589.9
150°	610.5	610.8	610.8	610.8	610.8	610.8	610.8	610.8	610.8	610.8	610.8
152.5°	628.9	629.0	629.1	629.2	629.3	629.5	629.6	630.0	630.4	630.7	631.1
155°	647.7	647.7	647.6	647.5	647.4	647.3	647.2	647.7	648.2	648.7	649.2
157.5°	663.7	663.6	663.6	663.6	663.6	663.6	663.6	664.0	664.4	664.7	665.1
160°	679.1	679.0	678.9	678.8	678.7	678.5	678.4	678.8	679.2	679.5	679.9
162.5°	691.7	691.5	691.4	691.3	691.2	691.0	690.9	691.7	692.4	693.2	693.9
165°	703.6	703.4	703.3	703.0	702.8	702.5	702.3	703.1	703.8	704.6	705.3
167.5°	712.8	712.5	712.5	712.5	712.5	712.5	712.5	713.3	714.0	714.8	715.5
170°	720.2	719.9	720.0	720.1	720.2	720.4	720.5	721.3	722.0	722.8	723.5
172.5°	726.4	726.1	726.1	726.1	726.1	726.1	726.1	727.0	727.9	728.8	729.7
175°	731.0	730.7	730.6	730.5	730.4	730.2	730.1	731.0	731.9	732.8	733.7
177.5°	733.3	733.0	733.0	733.0	733.0	733.0	733.0	733.9	734.7	735.6	736.5
180°	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1
2.5°	903.7	906.8	903.0	905.3	899.9	899.1	899.9	899.9	900.7	901.4	902.2
5°	852.9	852.1	847.5	844.4	842.1	844.4	846.0	847.5	846.0	847.5	848.3
7.5°	805.1	802.8	800.5	795.1	796.7	795.1	799.7	797.4	797.4	801.3	804.4
10°	762.8	758.1	756.6	750.4	745.8	745.0	750.4	752.7	755.0	756.6	762.8
12.5°	708.0	701.1	695.7	698.0	684.9	690.3	691.9	688.8	698.0	708.8	702.7
15°	649.5	650.3	639.5	635.6	624.8	627.9	628.7	636.4	644.1	643.3	652.6
17.5°	606.3	601.7	592.5	591.7	587.1	589.4	588.6	594.8	592.5	596.3	604.0
20°	566.3	563.2	555.5	552.4	554.0	552.4	553.2	554.0	556.3	564.7	563.2
22.5°	534.7	530.8	530.8	527.0	522.4	520.8	524.7	527.0	530.1	531.6	535.5
25°	507.0	503.9	500.0	497.7	493.9	494.6	496.9	500.0	502.3	505.4	508.5
27.5°	478.5	478.5	474.6	473.8	472.3	471.5	474.6	476.1	476.1	478.5	481.5
30°	456.1	456.1	452.3	451.5	450.7	450.7	453.0	453.8	454.6	456.9	458.4
32.5°	434.5	433.8	432.2	433.0	432.2	433.0	433.0	433.8	435.3	436.1	439.2
35°	414.5	415.3	413.7	413.7	413.0	413.7	415.3	416.0	416.8	418.4	418.4
37.5°	395.2	396.8	396.0	398.3	398.3	398.3	398.3	399.9	399.9	399.9	399.1
40°	378.3	378.3	377.5	379.1	380.6	380.6	381.4	381.4	382.1	382.1	381.4
42.5°	359.0	360.6	362.9	363.7	365.2	364.4	366.7	366.0	366.7	365.2	363.7
45°	341.3	341.3	344.4	347.5	348.2	348.2	348.2	349.8	348.2	345.9	345.2
47.5°	322.1	323.6	325.1	329.0	329.8	329.8	329.8	329.8	328.2	328.2	328.2
50°	302.8	303.6	304.3	305.9	308.2	307.4	307.4	307.4	310.5	307.4	308.2
52.5°	279.7	280.4	281.2	284.3	283.5	283.5	284.3	284.3	286.6	285.8	284.3
55°	256.6	256.6	258.1	258.1	258.1	259.6	260.4	262.0	261.2	262.0	262.7
57.5°	233.4	231.9	231.1	231.1	233.4	232.7	233.4	233.4	236.5	238.1	238.8
60°	206.5	206.5	205.7	201.1	201.1	200.3	202.6	204.2	205.7	212.6	211.9
62.5°	178.7	175.7	172.6	173.4	168.7	171.0	169.5	171.0	175.7	181.1	181.8
65°	151.0	148.7	145.6	144.8	143.3	145.6	144.8	145.6	147.9	151.0	154.9
67.5°	126.4	125.6	124.0	123.3	123.3	123.3	124.8	124.8	125.6	127.9	130.2
70°	107.9	107.1	107.9	106.3	107.1	106.3	107.1	107.9	108.6	109.4	111.7
72.5°	90.9	90.9	90.9	89.4	90.9	90.1	90.1	90.9	91.7	92.5	94.0
75°	72.4	70.9	69.3	67.8	67.0	68.6	69.3	68.6	70.9	74.0	74.0
77.5°	54.7	53.9	53.9	53.9	54.7	53.9	55.5	54.7	55.5	55.5	57.0
80°	42.4	41.6	42.4	42.4	41.6	43.1	42.4	42.4	43.1	43.9	43.1
82.5°	30.8	31.6	30.8	30.8	30.8	32.4	30.8	30.8	30.8	31.6	31.6
85°	19.3	19.3	19.3	19.3	20.0	19.3	20.0	19.3	20.8	20.0	20.0
87.5°	6.9	7.7	8.5	8.5	8.5	8.5	7.7	8.5	9.2	8.5	9.2
90°	15.9	16.0	16.3	16.5	16.8	17.0	16.8	16.5	16.3	16.0	15.9
92.5°	26.7	26.8	26.9	27.0	27.2	27.3	27.2	27.0	26.9	26.8	26.7
95°	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.9	44.9
97.5°	65.9	65.9	65.9	65.9	65.9	65.9	65.9	65.9	65.9	65.9	65.9
100°	88.1	88.1	88.1	88.1	88.1	88.1	88.1	88.1	88.1	88.1	88.1
102.5°	112.5	112.6	112.7	112.8	113.0	113.1	113.0	112.8	112.7	112.6	112.5
105°	136.9	137.1	137.5	137.8	138.2	138.6	138.2	137.8	137.5	137.1	136.9
107.5°	163.6	163.5	163.4	163.3	163.2	163.1	163.2	163.3	163.4	163.5	163.6
110°	188.1	188.3	188.7	189.0	189.4	189.8	189.4	189.0	188.7	188.3	188.1

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0
115°	246.0	245.9	245.8	245.7	245.6	245.5	245.6	245.7	245.8	245.9	246.0
117.5°	273.3	273.1	272.7	272.4	272.0	271.6	272.0	272.4	272.7	273.1	273.3
120°	301.1	301.2	301.5	301.8	302.0	302.3	302.0	301.8	301.5	301.2	301.1
122.5°	330.7	330.4	329.7	329.1	328.4	327.8	328.4	329.1	329.7	330.4	330.7
125°	359.1	359.0	358.7	358.5	358.2	358.0	358.2	358.5	358.7	359.0	359.1
127.5°	385.8	385.7	385.6	385.5	385.3	385.2	385.3	385.5	385.6	385.7	385.8
130°	414.2	413.9	413.4	412.9	412.4	411.9	412.4	412.9	413.4	413.9	414.2
132.5°	440.9	440.8	440.7	440.6	440.4	440.3	440.4	440.6	440.7	440.8	440.9
135°	467.6	467.4	467.0	466.7	466.3	465.9	466.3	466.7	467.0	467.4	467.6
137.5°	493.2	493.3	493.4	493.5	493.7	493.8	493.7	493.5	493.4	493.3	493.2
140°	519.3	519.2	519.1	519.0	518.9	518.8	518.9	519.0	519.1	519.2	519.3
142.5°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8
145°	567.6	567.4	567.0	566.7	566.3	565.9	566.3	566.7	567.0	567.4	567.6
147.5°	589.8	589.7	589.6	589.5	589.3	589.2	589.3	589.5	589.6	589.7	589.8
150°	610.8	610.7	610.6	610.5	610.3	610.2	610.3	610.5	610.6	610.7	610.8
152.5°	631.3	631.1	630.7	630.4	630.0	629.6	630.0	630.4	630.7	631.1	631.3
155°	649.4	649.2	648.7	648.2	647.7	647.2	647.7	648.2	648.7	649.2	649.4
157.5°	665.3	665.1	664.7	664.4	664.0	663.6	664.0	664.4	664.7	665.1	665.3
160°	680.1	679.8	679.2	678.5	677.9	677.3	677.9	678.5	679.2	679.8	680.1
162.5°	694.3	694.0	693.4	692.7	692.1	691.5	692.1	692.7	693.4	694.0	694.3
165°	705.7	705.4	704.9	704.4	703.9	703.4	703.9	704.4	704.9	705.4	705.7
167.5°	715.9	715.5	714.8	714.0	713.3	712.5	713.3	714.0	714.8	715.5	715.9
170°	723.9	723.5	722.6	721.7	720.8	719.9	720.8	721.7	722.6	723.5	723.9
172.5°	730.1	729.7	728.8	727.9	727.0	726.1	727.0	727.9	728.8	729.7	730.1
175°	734.1	733.7	732.8	731.9	731.0	730.1	731.0	731.9	732.8	733.7	734.1
177.5°	736.9	736.4	735.4	734.4	733.4	732.4	733.4	734.4	735.4	736.4	736.9
180°	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1	956.1
2.5°	905.3	909.1	907.6	902.2	904.5	909.1	913.8	919.9	923.8	926.9	928.4
5°	852.1	859.1	857.5	857.5	860.6	868.3	876.0	889.1	893.7	899.1	906.8
7.5°	805.1	810.5	815.1	816.7	821.3	831.3	841.3	856.0	867.5	873.7	878.3
10°	763.5	767.4	774.3	778.2	782.8	795.1	809.7	825.2	836.7	847.5	853.7
12.5°	710.4	725.8	735.0	741.2	747.3	765.8	777.4	794.3	808.2	818.2	827.5
15°	651.0	669.5	674.9	698.8	714.2	728.9	746.6	766.6	779.7	791.3	803.6
17.5°	601.0	614.1	620.2	645.6	658.7	681.9	707.3	732.7	752.7	761.2	773.5
20°	569.4	576.3	588.6	597.1	611.0	637.9	665.7	696.5	726.5	735.0	747.3
22.5°	537.0	546.3	554.7	566.3	577.1	595.6	623.3	657.2	689.6	705.0	719.6
25°	507.7	517.0	522.4	534.7	544.7	563.2	582.5	617.1	655.7	668.8	691.9
27.5°	484.6	490.0	499.3	504.6	516.2	533.2	550.9	577.1	614.8	637.2	659.5
30°	461.5	465.4	473.1	480.8	489.2	500.8	520.8	546.3	580.9	600.2	622.5
32.5°	438.4	444.6	449.2	454.6	463.8	477.7	491.6	516.2	543.9	565.5	587.9
35°	419.1	421.4	427.6	433.8	439.9	452.3	466.9	490.8	515.4	532.4	552.4
37.5°	398.3	402.2	406.8	409.1	419.1	426.8	442.2	460.7	490.0	500.8	520.8
40°	382.1	381.4	386.0	389.9	394.5	406.8	416.0	436.1	459.2	476.1	488.5
42.5°	362.1	362.1	363.7	368.3	374.4	382.1	392.9	409.9	433.8	446.1	460.7
45°	345.9	343.6	344.4	347.5	351.3	359.0	369.8	384.5	408.3	418.4	433.8
47.5°	326.7	324.4	324.4	327.4	330.5	335.9	344.4	361.3	380.6	393.7	405.3
50°	305.1	305.9	305.1	307.4	309.0	314.3	323.6	337.5	355.2	366.0	379.1
52.5°	285.1	283.5	282.8	284.3	287.4	291.2	301.2	313.6	330.5	341.3	352.9
55°	260.4	262.0	262.0	262.0	266.6	268.1	275.8	288.2	305.1	313.6	324.4
57.5°	238.1	237.3	238.8	238.1	241.9	247.3	253.5	262.7	279.7	288.2	298.2
60°	213.4	214.2	215.0	215.0	218.0	223.4	230.4	238.8	252.7	261.2	270.4
62.5°	183.4	187.2	191.1	192.6	197.2	201.1	205.7	215.0	227.3	233.4	241.9
65°	154.9	160.3	165.6	169.5	172.6	176.4	182.6	191.1	201.1	207.3	215.7
67.5°	130.2	134.1	141.0	144.8	151.0	155.6	159.5	166.4	178.7	181.1	188.0
70°	112.5	114.0	117.1	120.2	127.1	131.0	135.6	142.5	151.8	157.2	161.0
72.5°	94.8	95.5	97.1	100.2	103.2	107.9	113.3	119.4	127.9	130.2	135.6
75°	75.5	80.1	80.1	82.4	84.8	87.1	91.7	97.8	103.2	107.1	110.2
77.5°	56.2	58.6	60.1	63.9	67.0	69.3	72.4	77.0	80.1	83.2	85.5
80°	43.9	44.7	45.5	45.5	47.0	50.1	53.2	56.2	60.1	61.6	63.9
82.5°	32.4	32.4	32.4	33.9	34.7	35.4	35.4	37.0	40.8	42.4	44.7
85°	20.8	20.8	20.8	20.8	21.6	22.3	23.1	23.9	23.9	23.9	25.4
87.5°	8.5	10.0	9.2	10.0	10.0	10.0	10.0	10.8	10.8	11.6	11.6
90°	15.5	14.8	14.0	13.3	12.5	11.5	10.5	9.5	8.5	8.0	7.3
92.5°	26.5	26.1	25.8	25.4	25.0	24.4	23.8	23.1	22.5	22.2	21.4
95°	44.7	44.3	44.0	43.6	43.2	42.3	41.4	40.5	39.6	39.2	38.6
97.5°	65.6	65.1	64.6	64.1	63.6	62.6	61.6	60.6	59.6	59.1	58.6
100°	88.0	87.7	87.4	87.2	86.9	85.8	84.6	83.5	82.4	81.8	81.5
102.5°	112.3	111.9	111.6	111.2	110.8	109.8	108.8	107.8	106.8	106.3	106.2
105°	136.7	136.3	136.0	135.6	135.2	134.7	134.2	133.7	133.2	133.0	132.9
107.5°	163.4	162.9	162.4	161.9	161.4	161.3	161.1	161.0	160.9	160.8	160.7
110°	188.2	188.5	188.7	189.0	189.2	189.3	189.5	189.6	189.7	189.8	189.7

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	217.0	217.0	217.0	217.0	217.0	217.3	217.5	217.8	218.1	218.2	218.2
115°	246.1	246.2	246.3	246.5	246.6	246.8	247.1	247.3	247.6	247.7	247.7
117.5°	273.5	273.9	274.2	274.6	275.0	275.1	275.3	275.4	275.5	275.6	275.6
120°	301.4	302.1	302.7	303.4	304.0	304.4	304.8	305.1	305.5	305.7	305.4
122.5°	330.9	331.3	331.6	332.0	332.4	332.5	332.7	332.8	332.9	333.0	332.9
125°	359.2	359.5	359.7	360.0	360.2	360.3	360.5	360.6	360.7	360.8	360.8
127.5°	385.9	386.2	386.4	386.7	386.9	387.2	387.4	387.7	388.0	388.1	387.9
130°	414.3	414.6	414.8	415.1	415.3	415.3	415.3	415.3	415.3	415.3	415.1
132.5°	441.0	441.3	441.5	441.8	442.0	442.1	442.3	442.4	442.5	442.6	442.5
135°	467.7	468.0	468.3	468.5	468.8	468.8	468.8	468.8	468.8	468.8	468.4
137.5°	493.4	493.8	494.1	494.5	494.9	494.7	494.4	494.2	493.9	493.8	493.6
140°	519.4	519.5	519.6	519.8	519.9	519.9	519.9	519.9	519.9	519.9	519.8
142.5°	543.8	543.8	543.8	543.8	543.8	543.9	544.0	544.1	544.2	544.3	544.2
145°	567.7	567.8	567.9	568.1	568.2	568.1	567.9	567.8	567.7	567.6	567.3
147.5°	589.9	590.0	590.1	590.2	590.3	590.4	590.6	590.7	590.8	590.9	590.6
150°	610.8	610.8	610.8	610.8	610.8	610.8	610.8	610.8	610.8	610.8	610.5
152.5°	631.1	630.7	630.4	630.0	629.6	629.5	629.3	629.2	629.1	629.0	628.9
155°	649.2	648.7	648.2	647.7	647.2	647.3	647.4	647.5	647.6	647.7	647.7
157.5°	665.1	664.7	664.4	664.0	663.6	663.6	663.6	663.6	663.6	663.6	663.7
160°	679.9	679.5	679.2	678.8	678.4	678.5	678.7	678.8	678.9	679.0	679.1
162.5°	693.9	693.2	692.4	691.7	690.9	691.0	691.2	691.3	691.4	691.5	691.7
165°	705.3	704.6	703.8	703.1	702.3	702.5	702.8	703.0	703.3	703.4	703.6
167.5°	715.5	714.8	714.0	713.3	712.5	712.5	712.5	712.5	712.5	712.5	712.8
170°	723.5	722.8	722.0	721.3	720.5	720.4	720.2	720.1	720.0	719.9	720.2
172.5°	729.7	728.8	727.9	727.0	726.1	726.1	726.1	726.1	726.1	726.1	726.4
175°	733.7	732.8	731.9	731.0	730.1	730.2	730.4	730.5	730.6	730.7	731.0
177.5°	736.5	735.6	734.7	733.9	733.0	733.0	733.0	733.0	733.0	733.0	733.3
180°	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7	734.7

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	956.1	956.1	956.1	956.1
2.5°	934.6	939.2	946.9	957.7
5°	913.0	926.1	938.4	954.6
7.5°	893.7	909.1	926.1	949.2
10°	871.4	890.6	912.2	940.7
12.5°	845.2	872.2	896.8	927.6
15°	825.9	846.0	877.5	913.8
17.5°	799.0	825.9	857.5	898.4
20°	773.5	802.0	837.5	879.9
22.5°	746.6	778.9	814.4	859.8
25°	718.8	753.5	788.9	837.5
27.5°	693.4	725.0	765.1	814.4
30°	662.6	698.8	737.3	788.9
32.5°	632.5	670.3	709.6	761.2
35°	600.2	637.9	681.1	730.4
37.5°	568.6	610.2	649.5	697.3
40°	533.9	577.1	617.9	666.4
42.5°	500.0	544.7	585.5	627.2
45°	468.4	512.4	549.3	588.6
47.5°	438.4	477.7	515.4	550.9
50°	409.1	442.2	476.9	506.2
52.5°	378.3	409.9	437.6	463.8
55°	350.6	375.2	399.9	423.8
57.5°	317.4	342.1	363.7	382.1
60°	289.7	305.1	325.9	345.2
62.5°	258.1	275.8	292.0	304.3
65°	227.3	242.7	255.0	265.8
67.5°	201.1	210.3	219.6	231.1
70°	169.5	177.2	188.0	196.5
72.5°	142.5	148.7	154.1	164.1
75°	115.6	121.0	124.0	133.3
77.5°	89.4	94.8	97.1	102.5
80°	68.6	69.3	72.4	77.0
82.5°	47.0	48.5	49.3	53.2
85°	27.0	30.8	30.0	31.6
87.5°	11.6	12.3	13.9	15.4
90°	5.9	4.5	3.1	1.7
92.5°	19.7	18.1	16.4	14.8
95°	37.5	36.4	35.2	34.1
97.5°	57.6	56.5	55.5	54.5
100°	81.0	80.5	80.0	79.5
102.5°	106.1	106.0	105.8	105.7
105°	132.8	132.7	132.5	132.4
107.5°	160.6	160.5	160.3	160.2
110°	189.4	189.1	188.9	188.6

TEST NUMBER: P1026488

CATALOG NUMBER: S124RDIP-B575D590UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	218.2	218.2	218.2	218.2
115°	247.7	247.7	247.7	247.7
117.5°	275.6	275.6	275.6	275.6
120°	304.9	304.4	303.9	303.4
122.5°	332.8	332.7	332.5	332.4
125°	360.8	360.8	360.8	360.8
127.5°	387.5	387.2	386.8	386.4
130°	414.7	414.4	414.0	413.6
132.5°	442.2	442.0	441.7	441.5
135°	467.6	466.9	466.1	465.3
137.5°	493.2	492.9	492.5	492.1
140°	519.5	519.3	519.0	518.8
142.5°	543.9	543.7	543.4	543.2
145°	566.8	566.3	565.8	565.3
147.5°	590.0	589.3	588.7	588.1
150°	610.0	609.5	609.0	608.5
152.5°	628.6	628.3	628.1	627.8
155°	647.7	647.7	647.7	647.7
157.5°	664.0	664.3	664.5	664.8
160°	679.2	679.3	679.5	679.6
162.5°	692.1	692.4	692.8	693.2
165°	704.0	704.3	704.7	705.1
167.5°	713.3	713.8	714.3	714.8
170°	720.8	721.5	722.1	722.7
172.5°	726.9	727.4	727.9	728.4
175°	731.6	732.3	732.9	733.5
177.5°	733.9	734.6	735.2	735.8
180°	734.7	734.7	734.7	734.7

(END OF REPORT)