

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026573

Luminaire Tested: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026573
REPORT IS A COMBINATION OF REPORTS P999683 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7695.0 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	97	93	89	86	88	85	82	79	71	68	66	57	56	55	45	44	43
2	88	81	76	71	81	75	70	65	62	59	56	51	48	46	40	39	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	22	19
8	54	42	34	29	49	39	32	28	33	28	24	28	24	21	22	20	17
9	50	38	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10867	10867	10867	10867
5°	10868	12280	10885	9386
10°	10810	14156	10801	8163
15°	10681	15932	10681	6834
20°	10547	17274	10491	6018
25°	10383	17348	10335	5436
30°	10207	14751	10128	5034
35°	9961	11130	9834	4736
40°	9685	8066	9495	4502
45°	9231	6131	9002	4296
50°	8692	4955	8453	3994
55°	8108	4103	7842	3591
60°	7521	3469	7185	2986
65°	6785	2826	6569	2374
70°	6108	2291	5823	1928
75°	5354	1652	4983	1413
80°	4417	1095	4018	1038
85°	3202	562	2656	562

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13605 cd/sqm

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	1.7
10°-20°	389.7	5.1
20°-30°	610.5	7.9
30°-40°	677.9	8.8
40°-50°	600.7	7.8
50°-60°	468.1	6.1
60°-70°	306.2	4.0
70°-80°	150.3	2.0
80°-90°	38.9	0.5
90°-100°	430.2	5.6
100°-110°	898.3	11.7
110°-120°	798.5	10.4
120°-130°	672.1	8.7
130°-140°	560.8	7.3
140°-150°	428.1	5.6
150°-160°	301.0	3.9
160°-170°	177.0	2.3
170°-180°	57.6	0.7
0°-30°	1129.2	14.7
0°-40°	1807.1	23.5
0°-60°	2875.9	37.4
0°-90°	3371.3	43.8
90°-120°	2127.0	27.6
90°-150°	3788.0	49.2
90°-180°	4324.0	56.2
0°-180°	7695.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1333	1333	1333	1333	1333	
5°	1331	1540	1333	1177	1331	126
15°	1274	2040	1274	875	1274	359
25°	1167	2200	1162	690	1167	538
35°	1018	1355	1005	577	1018	636
45°	820	693	800	485	820	633
55°	591	414	571	362	591	528
65°	370	242	359	203	370	370
75°	186	112	173	96	186	197
85°	44	27	36	27	44	50
90°	1	24	1	24	1	6
95°	38	285	38	285	38	42
105°	136	1641	136	1641	136	145
115°	240	1576	240	1576	240	238
125°	335	1257	335	1257	335	298
135°	398	1124	398	1124	398	307
145°	458	918	458	918	458	288
155°	521	769	521	769	521	240
165°	568	671	568	671	568	160
175°	592	604	592	604	592	56
180°	594	594	594	594	594	

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1334.9	1346.7	1353.1	1358.5	1369.2	1373.5	1382.1	1384.3	1392.9	1391.8	1388.6
5°	1330.6	1351.0	1366.0	1382.1	1401.5	1412.2	1424.0	1441.2	1449.8	1461.6	1469.1
7.5°	1323.1	1351.0	1375.7	1400.4	1431.5	1448.7	1463.8	1490.6	1513.2	1532.5	1554.0
10°	1311.3	1346.7	1383.2	1416.5	1459.5	1479.9	1502.4	1542.2	1573.3	1600.1	1634.5
12.5°	1293.0	1342.4	1383.2	1428.3	1483.1	1511.0	1541.1	1588.3	1624.8	1668.9	1711.8
15°	1273.7	1328.4	1382.1	1441.2	1503.5	1535.7	1565.8	1629.1	1685.0	1735.5	1782.7
17.5°	1252.2	1312.3	1371.4	1436.9	1512.1	1551.8	1587.3	1663.5	1724.7	1790.2	1837.5
20°	1226.4	1291.9	1359.6	1432.6	1517.5	1561.5	1601.2	1688.2	1755.9	1826.7	1885.8
22.5°	1198.5	1269.4	1343.5	1422.9	1511.0	1559.3	1605.5	1698.9	1777.3	1842.8	1922.3
25°	1167.4	1242.5	1318.8	1402.5	1501.3	1554.0	1601.2	1693.6	1777.3	1863.3	1940.6
27.5°	1135.1	1212.5	1291.9	1380.0	1480.9	1532.5	1586.2	1675.3	1773.0	1866.5	1944.9
30°	1099.7	1174.9	1258.6	1342.4	1449.8	1501.3	1556.1	1652.8	1759.1	1852.5	1937.4
32.5°	1061.0	1138.4	1217.8	1304.8	1410.1	1465.9	1516.4	1625.9	1734.4	1826.7	1906.2
35°	1018.1	1091.1	1166.3	1255.4	1359.6	1410.1	1470.2	1584.0	1693.6	1791.3	1842.8
37.5°	971.9	1041.7	1111.5	1199.6	1299.4	1360.7	1419.7	1534.6	1650.6	1716.1	1743.0
40°	928.9	990.2	1051.4	1136.2	1237.2	1300.5	1360.7	1479.9	1581.9	1632.4	1612.0
42.5°	874.2	937.5	992.3	1070.7	1172.7	1231.8	1293.0	1416.5	1499.2	1519.6	1469.1
45°	820.5	873.1	925.7	1002.0	1109.4	1159.8	1225.3	1340.3	1409.0	1390.7	1316.6
47.5°	767.9	810.8	860.2	934.3	1031.0	1091.1	1152.3	1252.2	1300.5	1274.7	1171.6
50°	705.6	748.5	800.1	864.5	957.9	1015.9	1064.3	1156.6	1193.1	1129.8	1005.2
52.5°	646.5	684.1	728.1	788.3	877.4	930.0	982.6	1062.1	1073.9	1000.9	869.9
55°	590.7	620.7	666.9	715.2	796.8	852.7	889.2	956.9	953.6	862.4	749.6
57.5°	532.7	560.6	591.7	642.2	719.5	761.4	801.1	860.2	829.1	751.7	640.1
60°	481.1	497.2	528.4	576.7	642.2	678.7	709.9	742.1	715.2	631.5	545.6
62.5°	424.2	442.5	465.0	503.7	561.7	596.0	618.6	632.5	604.6	540.2	461.8
65°	370.5	386.6	410.2	444.6	488.6	514.4	526.2	535.9	520.9	447.8	385.5
67.5°	322.2	332.9	354.4	376.9	424.2	430.6	446.8	451.0	421.0	365.1	315.7
70°	273.8	284.6	294.3	321.1	342.6	354.4	357.6	357.6	327.5	291.0	250.2
72.5°	228.7	235.2	244.9	263.1	274.9	283.5	287.8	282.4	254.5	224.4	194.4
75°	185.8	189.0	197.6	209.4	219.1	215.9	214.8	208.3	187.9	166.5	149.3
77.5°	142.8	145.0	154.6	157.9	157.9	161.1	156.8	150.3	133.2	117.1	109.5
80°	107.4	110.6	111.7	113.8	111.7	111.7	108.5	97.7	89.1	81.6	76.2
82.5°	74.1	76.2	77.3	74.1	76.2	73.0	67.7	60.1	54.8	53.7	51.5
85°	44.0	45.1	44.0	44.0	40.8	39.7	35.4	34.4	32.2	32.2	31.1
87.5°	21.5	20.4	18.3	16.1	16.1	15.0	16.1	14.0	16.1	15.0	14.0
90°	1.2	3.5	7.0	8.2	9.3	9.3	9.3	16.3	16.3	18.7	21.0
92.5°	16.3	23.3	36.2	53.6	74.6	89.8	105.0	177.3	290.4	400.0	457.2
95°	38.5	42.0	53.6	68.8	96.8	121.3	145.8	247.3	438.5	717.3	950.5
97.5°	64.1	64.1	74.6	88.6	113.1	134.1	155.1	235.6	400.0	686.9	1017.0
100°	88.6	88.6	96.8	110.8	133.0	151.6	170.3	239.1	370.9	608.8	937.7
102.5°	112.0	114.3	121.3	134.1	155.1	172.6	190.1	250.8	362.7	556.3	838.6
105°	136.5	140.0	145.8	159.8	180.8	197.7	214.6	270.6	367.4	530.7	765.1
107.5°	163.3	165.6	171.4	186.6	206.4	223.4	240.3	291.6	381.4	523.7	717.3
110°	190.1	192.4	198.3	212.3	233.3	249.0	264.7	316.1	397.7	526.0	695.1

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	215.8	218.1	225.1	237.9	258.9	274.6	290.4	339.4	415.2	533.0	684.6
115°	240.3	243.8	251.9	263.6	285.7	301.4	317.2	363.9	433.9	542.3	682.3
117.5°	265.9	269.4	276.4	289.2	310.2	326.5	342.9	387.2	452.5	551.7	681.1
120°	291.6	293.9	302.1	314.9	334.7	351.0	367.4	411.7	472.3	562.2	681.1
122.5°	314.9	317.2	325.4	337.1	359.2	375.0	390.7	435.0	491.0	572.7	680.0
125°	334.7	339.4	346.4	359.2	381.4	397.7	414.0	456.0	509.7	583.1	678.8
127.5°	353.4	356.9	365.1	379.0	402.4	418.7	435.0	475.8	526.0	591.3	676.5
130°	368.5	373.2	382.5	400.0	422.2	439.1	456.0	495.7	541.2	600.6	675.3
132.5°	383.7	387.2	400.0	416.4	440.9	456.6	472.3	512.0	556.3	608.8	674.1
135°	397.7	402.4	414.0	433.9	458.4	473.6	488.7	527.2	569.2	617.0	673.0
137.5°	411.7	416.4	429.2	447.9	473.5	488.1	502.7	538.8	578.5	621.6	673.0
140°	426.9	430.4	443.2	463.0	487.5	501.5	515.5	550.5	587.8	627.5	671.8
142.5°	443.2	446.7	458.4	477.0	500.3	513.8	527.2	561.0	594.8	632.1	671.8
145°	458.4	461.9	473.5	489.8	512.0	524.8	537.7	568.0	599.5	633.3	669.5
147.5°	475.8	477.0	487.5	505.0	523.7	535.4	547.0	576.2	604.1	634.5	666.0
150°	492.2	493.3	502.7	516.7	534.2	545.2	556.3	582.0	607.6	634.5	662.5
152.5°	507.3	507.3	516.7	529.5	544.7	554.6	564.5	586.6	610.0	632.1	656.6
155°	521.3	522.5	529.5	541.2	554.0	562.8	571.5	591.3	611.1	629.8	650.8
157.5°	535.3	535.3	542.3	551.7	563.3	570.3	577.3	594.8	611.1	627.5	645.0
160°	548.2	548.2	552.8	561.0	570.3	576.7	583.1	597.1	611.1	624.0	638.0
162.5°	559.8	558.7	562.2	569.2	577.3	582.0	586.6	599.5	611.1	620.5	631.0
165°	568.0	568.0	570.3	576.2	582.0	585.5	589.0	599.5	608.8	615.8	624.0
167.5°	577.3	576.2	577.3	582.0	585.5	588.4	591.3	599.5	606.5	611.1	617.0
170°	583.1	582.0	583.1	586.6	589.0	590.8	592.5	598.3	604.1	606.5	610.0
172.5°	589.0	587.8	587.8	590.1	591.3	592.4	593.6	597.1	601.8	601.8	603.0
175°	592.5	591.3	591.3	592.5	593.6	593.6	593.6	596.0	599.5	598.3	598.3
177.5°	594.8	593.6	592.5	593.6	593.6	593.6	593.6	594.8	597.1	594.8	594.8
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1397.2	1409.0	1410.1	1420.8	1417.6	1412.2	1421.9	1415.4	1428.3	1424.0	1429.4
5°	1478.8	1494.9	1508.9	1517.5	1532.5	1529.3	1545.4	1540.0	1551.8	1540.0	1555.0
7.5°	1574.4	1601.2	1615.2	1637.7	1644.2	1645.2	1664.6	1668.9	1676.4	1668.9	1677.5
10°	1667.8	1700.0	1732.2	1750.5	1762.3	1778.4	1795.6	1803.1	1808.5	1801.0	1806.3
12.5°	1752.6	1803.1	1838.6	1875.1	1883.7	1897.6	1915.9	1913.7	1935.2	1930.9	1940.6
15°	1831.0	1886.9	1929.8	1958.8	1982.5	1994.3	2028.6	2030.8	2029.7	2040.4	2034.0
17.5°	1900.8	1948.1	2009.3	2046.9	2075.9	2075.9	2095.2	2135.0	2131.7	2130.7	2137.1
20°	1957.8	2011.5	2068.4	2131.7	2155.4	2159.7	2186.5	2206.9	2210.1	2210.1	2210.1
22.5°	2000.7	2064.1	2125.3	2170.4	2188.7	2203.7	2227.3	2240.2	2244.5	2242.3	2244.5
25°	2022.2	2082.3	2144.6	2185.4	2196.2	2204.8	2206.9	2214.4	2213.4	2200.5	2208.0
27.5°	2026.5	2084.5	2125.3	2136.0	2130.7	2125.3	2090.9	2094.1	2084.5	2065.1	2072.7
30°	2007.2	2038.3	2037.2	2003.9	1994.3	1971.7	1940.6	1894.4	1856.8	1840.7	1846.1
32.5°	1937.4	1937.4	1898.7	1823.5	1790.2	1749.4	1693.6	1651.7	1602.3	1591.6	1612.0
35°	1840.7	1785.9	1715.1	1616.3	1565.8	1535.7	1439.1	1409.0	1367.1	1355.3	1365.0
37.5°	1690.4	1599.1	1496.0	1403.6	1360.7	1307.0	1222.1	1179.2	1149.1	1128.7	1138.4
40°	1521.7	1411.1	1303.7	1189.9	1142.7	1098.6	1035.3	996.6	948.3	950.4	953.6
42.5°	1360.7	1230.7	1110.4	1005.2	960.1	923.6	879.5	832.3	815.1	809.7	804.4
45°	1189.9	1051.4	938.6	860.2	819.4	785.0	744.2	717.4	697.0	692.7	698.0
47.5°	1028.8	911.8	804.4	731.3	698.0	680.9	648.6	623.9	611.1	600.3	606.8
50°	882.8	773.2	687.3	626.1	602.5	590.7	560.6	547.7	534.8	531.6	530.5
52.5°	762.5	669.1	595.0	545.6	527.3	520.9	498.3	480.0	469.3	472.5	474.7
55°	652.9	573.5	515.5	475.7	460.7	453.2	437.1	424.2	416.7	413.5	415.6
57.5°	556.3	487.6	445.7	413.5	401.6	398.4	381.2	376.9	371.6	368.4	368.4
60°	468.2	419.9	381.2	363.0	350.1	346.9	334.0	328.6	327.5	324.3	322.2
62.5°	394.1	354.4	327.5	308.2	302.8	301.8	293.2	286.7	283.5	281.4	281.4
65°	329.7	300.7	278.1	264.2	259.9	257.7	248.1	245.9	243.8	241.6	240.6
67.5°	274.9	249.1	233.0	223.4	218.0	219.1	213.7	209.4	209.4	208.3	207.3
70°	222.3	206.2	192.2	186.9	184.7	182.6	180.4	177.2	176.1	176.1	176.1
72.5°	175.0	164.3	156.8	153.6	151.4	149.3	147.1	147.1	147.1	146.1	146.1
75°	134.2	129.9	124.6	121.4	121.4	123.5	120.3	117.1	113.8	111.7	112.8
77.5°	100.9	98.8	95.6	90.2	91.3	89.1	89.1	87.0	88.1	88.1	85.9
80°	74.1	70.9	69.8	66.6	67.7	66.6	65.5	65.5	63.4	63.4	63.4
82.5°	51.5	48.3	48.3	47.3	46.2	46.2	45.1	45.1	46.2	44.0	44.0
85°	31.1	30.1	30.1	27.9	27.9	27.9	27.9	29.0	27.9	26.8	26.8
87.5°	14.0	15.0	14.0	12.9	12.9	12.9	11.8	11.8	10.7	11.8	11.8
90°	19.8	21.0	22.2	23.3	23.3	23.3	24.5	25.7	24.5	24.5	24.5
92.5°	380.2	281.1	209.9	165.6	151.0	136.5	119.0	110.8	106.1	106.1	106.1
95°	977.4	864.2	683.4	527.2	470.6	414.0	356.9	320.7	299.7	284.6	299.7
97.5°	1225.8	1244.4	1154.6	1026.3	961.0	895.7	816.4	746.4	711.4	683.4	711.4
100°	1236.3	1406.6	1429.9	1372.7	1329.6	1286.4	1185.0	1113.8	1078.8	1069.5	1078.8
102.5°	1148.8	1398.4	1537.2	1572.2	1560.5	1548.8	1496.4	1449.7	1412.4	1405.4	1412.4
105°	1039.2	1306.3	1508.0	1623.5	1647.4	1671.3	1673.6	1664.3	1648.0	1641.0	1648.0
107.5°	949.4	1193.1	1411.2	1572.2	1621.2	1670.1	1721.5	1742.4	1751.8	1752.9	1751.8
110°	885.2	1092.8	1294.6	1463.7	1527.8	1592.0	1674.8	1723.8	1744.8	1755.3	1744.8

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	849.1	1019.3	1192.0	1349.4	1413.6	1477.7	1574.5	1636.3	1667.8	1686.5	1667.8
115°	829.2	975.0	1118.5	1254.9	1310.9	1366.9	1459.0	1529.0	1566.3	1575.7	1566.3
117.5°	818.7	949.4	1070.7	1181.5	1230.4	1279.4	1361.1	1421.7	1461.4	1467.2	1461.4
120°	810.6	933.0	1041.5	1134.8	1176.2	1217.6	1284.1	1335.4	1365.7	1378.6	1365.7
122.5°	801.2	919.0	1022.8	1105.6	1140.6	1175.6	1229.3	1271.3	1295.8	1308.6	1295.8
125°	790.7	902.7	1003.0	1083.5	1115.6	1147.6	1194.3	1228.1	1250.3	1257.3	1250.3
127.5°	776.8	884.1	980.9	1061.3	1091.6	1122.0	1168.6	1199.0	1217.6	1224.6	1217.6
130°	763.9	860.7	952.9	1032.2	1063.1	1094.0	1141.8	1171.0	1189.6	1196.6	1189.6
132.5°	752.3	836.2	921.4	998.3	1029.2	1060.2	1106.8	1140.6	1158.1	1165.1	1158.1
135°	740.6	814.1	889.9	961.0	990.2	1019.3	1066.0	1098.7	1117.3	1124.3	1117.3
137.5°	730.1	793.1	859.6	921.4	948.2	975.0	1019.3	1053.2	1068.3	1076.5	1068.3
140°	721.9	775.6	830.4	882.9	907.4	931.9	972.7	998.3	1014.7	1024.0	1014.7
142.5°	714.9	759.3	805.9	849.1	869.5	889.9	924.9	948.2	962.2	968.0	962.2
145°	706.8	744.1	783.8	818.7	835.0	851.4	880.6	900.4	912.0	917.9	912.0
147.5°	699.8	731.3	763.9	793.1	806.5	819.9	842.1	859.6	868.9	871.2	868.9
150°	691.6	719.6	746.4	769.8	780.2	790.7	809.4	824.6	831.6	832.7	831.6
152.5°	682.3	706.8	728.9	749.9	758.1	766.3	781.4	793.1	796.6	797.7	796.6
155°	673.0	693.9	712.6	730.1	737.1	744.1	755.8	765.1	768.6	768.6	768.6
157.5°	663.6	680.0	696.3	711.4	717.2	723.1	732.4	739.4	741.8	741.8	741.8
160°	653.1	667.1	680.0	692.8	697.4	702.1	709.1	716.1	717.3	717.3	717.3
162.5°	643.8	654.3	664.8	674.1	678.2	682.3	686.9	693.9	695.1	693.9	695.1
165°	633.3	642.6	649.6	657.8	660.7	663.6	668.3	673.0	671.8	670.6	671.8
167.5°	624.0	631.0	636.8	643.8	645.6	647.3	649.6	653.1	653.1	652.0	653.1
170°	614.6	620.5	624.0	628.6	630.4	632.1	634.5	635.6	634.5	634.5	634.5
172.5°	606.5	611.1	613.5	615.8	617.0	618.1	619.3	620.5	619.3	617.0	619.3
175°	600.6	603.0	604.1	606.5	606.5	606.5	606.5	608.8	606.5	604.1	606.5
177.5°	596.0	597.1	598.3	598.3	598.9	599.5	598.3	599.5	597.1	594.8	597.1
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1432.6	1425.1	1424.0	1424.0	1412.2	1418.6	1405.8	1391.8	1385.4	1385.4	1373.5
5°	1551.8	1544.3	1536.8	1525.0	1525.0	1518.5	1498.1	1477.7	1462.7	1449.8	1435.8
7.5°	1674.2	1666.7	1645.2	1633.4	1639.9	1627.0	1600.1	1565.8	1540.0	1519.6	1490.6
10°	1807.4	1787.0	1776.3	1769.8	1747.3	1733.3	1702.2	1651.7	1619.5	1592.6	1555.0
12.5°	1915.9	1922.3	1881.5	1884.7	1862.2	1842.8	1794.5	1746.2	1697.9	1660.3	1604.4
15°	2032.9	2013.6	1988.9	1969.6	1962.1	1938.4	1897.6	1833.2	1780.6	1721.5	1658.1
17.5°	2125.3	2110.3	2086.6	2068.4	2052.3	1995.3	1961.0	1904.1	1832.1	1774.1	1696.8
20°	2203.7	2189.7	2156.4	2144.6	2115.6	2074.8	2025.4	1937.4	1872.9	1809.6	1734.4
22.5°	2237.0	2223.0	2194.0	2179.0	2160.7	2121.0	2073.7	1990.0	1910.5	1831.0	1751.6
25°	2209.1	2209.1	2195.1	2189.7	2173.6	2138.2	2089.9	2019.0	1934.1	1848.2	1753.7
27.5°	2073.7	2100.6	2110.3	2115.6	2115.6	2116.7	2083.4	2014.7	1932.0	1848.2	1749.4
30°	1878.3	1923.4	1963.1	1974.9	1995.3	2017.9	2031.9	1998.6	1924.5	1836.4	1737.6
32.5°	1632.4	1690.4	1764.5	1782.7	1810.6	1878.3	1915.9	1929.8	1889.0	1811.7	1706.5
35°	1387.5	1460.5	1505.6	1561.5	1587.3	1687.1	1770.9	1821.4	1811.7	1765.5	1669.9
37.5°	1173.8	1215.7	1270.4	1329.5	1381.1	1476.6	1580.8	1678.5	1718.3	1695.7	1623.8
40°	968.7	1018.1	1083.6	1131.9	1167.4	1262.9	1391.8	1498.1	1585.1	1599.1	1555.0
42.5°	823.7	873.1	912.8	965.5	993.4	1085.7	1199.6	1332.7	1435.8	1490.6	1471.3
45°	712.0	742.1	774.3	804.4	838.7	920.4	1025.6	1171.6	1287.6	1365.0	1372.5
47.5°	614.3	641.1	669.1	697.0	716.3	779.7	876.3	995.5	1122.2	1228.6	1270.4
50°	545.6	558.4	578.8	595.0	617.5	672.3	749.6	852.7	986.9	1101.8	1156.6
52.5°	477.9	494.0	510.1	524.1	539.1	577.8	648.6	737.8	853.8	971.9	1039.6
55°	421.0	433.9	448.9	458.6	467.2	501.5	555.2	623.9	723.8	835.5	919.3
57.5°	374.8	380.2	393.1	398.4	408.1	436.0	474.7	535.9	616.4	724.9	793.6
60°	324.3	335.1	344.7	349.0	356.5	375.9	402.7	459.6	529.4	608.9	687.3
62.5°	283.5	287.8	295.3	300.7	306.1	326.5	349.0	392.0	444.6	511.2	583.1
65°	245.9	248.1	252.4	259.9	263.1	278.1	291.0	322.2	371.6	422.1	494.0
67.5°	207.3	209.4	214.8	219.1	222.3	232.0	245.9	268.5	295.3	351.2	390.9
70°	177.2	177.2	180.4	182.6	185.8	190.1	197.6	214.8	239.5	274.9	311.4
72.5°	148.2	148.2	148.2	151.4	151.4	154.6	158.9	170.8	187.9	215.9	239.5
75°	114.9	116.0	118.1	118.1	119.2	123.5	126.7	129.9	138.5	156.8	178.3
77.5°	87.0	89.1	90.2	88.1	90.2	90.2	94.5	98.8	103.1	108.5	124.6
80°	64.4	65.5	63.4	64.4	64.4	66.6	68.7	67.7	69.8	76.2	80.5
82.5°	43.0	44.0	44.0	44.0	44.0	47.3	47.3	46.2	47.3	48.3	49.4
85°	26.8	25.8	25.8	26.8	25.8	25.8	26.8	27.9	26.8	27.9	29.0
87.5°	11.8	11.8	11.8	11.8	10.7	10.7	11.8	10.7	11.8	10.7	9.7
90°	25.7	24.5	23.3	23.3	23.3	22.2	21.0	19.8	21.0	18.7	16.3
92.5°	110.8	119.0	136.5	151.0	165.6	209.9	281.1	380.2	457.2	400.0	290.4
95°	320.7	356.9	414.0	470.6	527.2	683.4	864.2	977.4	950.5	717.3	438.5
97.5°	746.4	816.4	895.7	961.0	1026.3	1154.6	1244.4	1225.8	1017.0	686.9	400.0
100°	1113.8	1185.0	1286.4	1329.6	1372.7	1429.9	1406.6	1236.3	937.7	608.8	370.9
102.5°	1449.7	1496.4	1548.8	1560.5	1572.2	1537.2	1398.4	1148.8	838.6	556.3	362.7
105°	1664.3	1673.6	1671.3	1647.4	1623.5	1508.0	1306.3	1039.2	765.1	530.7	367.4
107.5°	1742.4	1721.5	1670.1	1621.2	1572.2	1411.2	1193.1	949.4	717.3	523.7	381.4
110°	1723.8	1674.8	1592.0	1527.8	1463.7	1294.6	1092.8	885.2	695.1	526.0	397.7

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1636.3	1574.5	1477.7	1413.6	1349.4	1192.0	1019.3	849.1	684.6	533.0	415.2
115°	1529.0	1459.0	1366.9	1310.9	1254.9	1118.5	975.0	829.2	682.3	542.3	433.9
117.5°	1421.7	1361.1	1279.4	1230.4	1181.5	1070.7	949.4	818.7	681.1	551.7	452.5
120°	1335.4	1284.1	1217.6	1176.2	1134.8	1041.5	933.0	810.6	681.1	562.2	472.3
122.5°	1271.3	1229.3	1175.6	1140.6	1105.6	1022.8	919.0	801.2	680.0	572.7	491.0
125°	1228.1	1194.3	1147.6	1115.6	1083.5	1003.0	902.7	790.7	678.8	583.1	509.7
127.5°	1199.0	1168.6	1122.0	1091.6	1061.3	980.9	884.1	776.8	676.5	591.3	526.0
130°	1171.0	1141.8	1094.0	1063.1	1032.2	952.9	860.7	763.9	675.3	600.6	541.2
132.5°	1140.6	1106.8	1060.2	1029.2	998.3	921.4	836.2	752.3	674.1	608.8	556.3
135°	1098.7	1066.0	1019.3	990.2	961.0	889.9	814.1	740.6	673.0	617.0	569.2
137.5°	1053.2	1019.3	975.0	948.2	921.4	859.6	793.1	730.1	673.0	621.6	578.5
140°	998.3	972.7	931.9	907.4	882.9	830.4	775.6	721.9	671.8	627.5	587.8
142.5°	948.2	924.9	889.9	869.5	849.1	805.9	759.3	714.9	671.8	632.1	594.8
145°	900.4	880.6	851.4	835.0	818.7	783.8	744.1	706.8	669.5	633.3	599.5
147.5°	859.6	842.1	819.9	806.5	793.1	763.9	731.3	699.8	666.0	634.5	604.1
150°	824.6	809.4	790.7	780.2	769.8	746.4	719.6	691.6	662.5	634.5	607.6
152.5°	793.1	781.4	766.3	758.1	749.9	728.9	706.8	682.3	656.6	632.1	610.0
155°	765.1	755.8	744.1	737.1	730.1	712.6	693.9	673.0	650.8	629.8	611.1
157.5°	739.4	732.4	723.1	717.2	711.4	696.3	680.0	663.6	645.0	627.5	611.1
160°	716.1	709.1	702.1	697.4	692.8	680.0	667.1	653.1	638.0	624.0	611.1
162.5°	693.9	686.9	682.3	678.2	674.1	664.8	654.3	643.8	631.0	620.5	611.1
165°	673.0	668.3	663.6	660.7	657.8	649.6	642.6	633.3	624.0	615.8	608.8
167.5°	653.1	649.6	647.3	645.6	643.8	636.8	631.0	624.0	617.0	611.1	606.5
170°	635.6	634.5	632.1	630.4	628.6	624.0	620.5	614.6	610.0	606.5	604.1
172.5°	620.5	619.3	618.1	617.0	615.8	613.5	611.1	606.5	603.0	601.8	601.8
175°	608.8	606.5	606.5	606.5	606.5	604.1	603.0	600.6	598.3	598.3	599.5
177.5°	599.5	598.3	599.5	598.9	598.3	598.3	597.1	596.0	594.8	594.8	597.1
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1367.1	1361.7	1358.5	1357.4	1347.8	1342.4	1339.2	1337.0	1333.8	1325.2	1317.7
5°	1418.6	1403.6	1396.1	1387.5	1372.5	1355.3	1341.3	1332.7	1322.0	1304.8	1288.7
7.5°	1467.0	1444.4	1429.4	1417.6	1391.8	1363.9	1341.3	1323.1	1302.7	1279.0	1256.5
10°	1517.5	1480.9	1461.6	1443.3	1405.8	1369.2	1337.0	1310.2	1281.2	1250.0	1225.3
12.5°	1557.2	1508.9	1487.4	1461.6	1415.4	1372.5	1331.7	1295.1	1257.6	1224.3	1188.8
15°	1603.4	1543.2	1518.5	1485.2	1421.9	1366.0	1313.4	1273.7	1235.0	1185.6	1148.0
17.5°	1630.2	1560.4	1525.0	1496.0	1427.2	1359.6	1298.4	1249.0	1203.9	1154.5	1114.7
20°	1657.1	1577.6	1537.9	1497.0	1415.4	1343.5	1279.0	1220.0	1172.7	1119.0	1078.2
22.5°	1665.7	1573.3	1531.4	1493.8	1407.9	1327.4	1253.3	1193.1	1138.4	1084.7	1038.5
25°	1665.7	1572.2	1522.8	1474.5	1384.3	1301.6	1227.5	1162.0	1100.8	1047.1	1000.9
27.5°	1648.5	1550.7	1499.2	1455.2	1361.7	1272.6	1196.3	1124.4	1065.3	1011.6	959.0
30°	1627.0	1519.6	1468.0	1415.4	1325.2	1240.4	1157.7	1091.1	1028.8	967.6	920.4
32.5°	1600.1	1486.3	1429.4	1375.7	1280.1	1192.1	1115.8	1050.3	991.2	927.9	875.2
35°	1561.5	1436.9	1373.5	1326.3	1233.9	1142.7	1069.6	1005.2	948.3	882.8	825.8
37.5°	1512.1	1391.8	1327.4	1269.4	1173.8	1090.0	1021.3	959.0	903.2	843.0	779.7
40°	1454.1	1328.4	1272.6	1211.4	1110.4	1031.0	966.5	910.7	854.8	797.9	736.7
42.5°	1388.6	1264.0	1201.7	1142.7	1046.0	967.6	907.5	857.0	805.4	752.8	687.3
45°	1310.2	1193.1	1133.0	1077.1	983.7	903.2	848.4	800.1	756.0	702.3	644.4
47.5°	1222.1	1120.1	1058.9	998.7	907.5	837.7	784.0	743.2	705.6	651.9	599.2
50°	1136.2	1035.3	985.9	924.6	840.9	775.4	720.6	686.2	657.2	604.6	557.4
52.5°	1027.7	951.5	904.2	851.6	771.1	704.5	661.5	631.5	597.1	556.3	514.4
55°	932.2	861.3	823.7	774.3	694.8	635.8	599.2	571.3	544.5	508.0	474.7
57.5°	823.7	779.7	742.1	699.1	620.7	570.3	538.0	514.4	489.7	459.6	432.8
60°	709.9	689.5	652.9	618.6	552.0	508.0	481.1	459.6	436.0	411.3	388.8
62.5°	608.9	597.1	575.6	548.8	486.5	448.9	422.1	405.9	388.8	366.2	344.7
65°	513.3	508.0	487.6	468.2	425.3	392.0	368.4	358.7	339.4	322.2	302.8
67.5°	428.5	422.1	410.2	401.6	365.1	334.0	322.2	309.3	293.2	280.3	264.2
70°	342.6	341.5	334.0	323.3	303.9	281.4	269.6	261.0	244.9	235.2	223.4
72.5°	266.3	271.7	265.3	261.0	248.1	232.0	221.2	215.9	203.0	195.5	186.9
75°	198.7	203.0	206.2	198.7	195.5	187.9	178.3	172.9	166.5	155.7	152.5
77.5°	135.3	145.0	145.0	147.1	148.2	143.9	136.4	132.1	124.6	122.4	118.1
80°	89.1	97.7	98.8	100.9	104.2	104.2	98.8	97.7	90.2	89.1	85.9
82.5°	51.5	59.1	63.4	66.6	65.5	69.8	65.5	64.4	60.1	60.1	58.0
85°	27.9	29.0	31.1	33.3	35.4	37.6	37.6	36.5	35.4	34.4	32.2
87.5°	10.7	10.7	11.8	10.7	11.8	14.0	15.0	15.0	14.0	12.9	10.7
90°	16.3	9.3	9.3	9.3	8.2	7.0	3.5	1.2	3.5	7.0	8.2
92.5°	177.3	105.0	89.8	74.6	53.6	36.2	23.3	16.3	23.3	36.2	53.6
95°	247.3	145.8	121.3	96.8	68.8	53.6	42.0	38.5	42.0	53.6	68.8
97.5°	235.6	155.1	134.1	113.1	88.6	74.6	64.1	64.1	64.1	74.6	88.6
100°	239.1	170.3	151.6	133.0	110.8	96.8	88.6	88.6	88.6	96.8	110.8
102.5°	250.8	190.1	172.6	155.1	134.1	121.3	114.3	112.0	114.3	121.3	134.1
105°	270.6	214.6	197.7	180.8	159.8	145.8	140.0	136.5	140.0	145.8	159.8
107.5°	291.6	240.3	223.4	206.4	186.6	171.4	165.6	163.3	165.6	171.4	186.6
110°	316.1	264.7	249.0	233.3	212.3	198.3	192.4	190.1	192.4	198.3	212.3

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	339.4	290.4	274.6	258.9	237.9	225.1	218.1	215.8	218.1	225.1	237.9
115°	363.9	317.2	301.4	285.7	263.6	251.9	243.8	240.3	243.8	251.9	263.6
117.5°	387.2	342.9	326.5	310.2	289.2	276.4	269.4	265.9	269.4	276.4	289.2
120°	411.7	367.4	351.0	334.7	314.9	302.1	293.9	291.6	293.9	302.1	314.9
122.5°	435.0	390.7	375.0	359.2	337.1	325.4	317.2	314.9	317.2	325.4	337.1
125°	456.0	414.0	397.7	381.4	359.2	346.4	339.4	334.7	339.4	346.4	359.2
127.5°	475.8	435.0	418.7	402.4	379.0	365.1	356.9	353.4	356.9	365.1	379.0
130°	495.7	456.0	439.1	422.2	400.0	382.5	373.2	368.5	373.2	382.5	400.0
132.5°	512.0	472.3	456.6	440.9	416.4	400.0	387.2	383.7	387.2	400.0	416.4
135°	527.2	488.7	473.6	458.4	433.9	414.0	402.4	397.7	402.4	414.0	433.9
137.5°	538.8	502.7	488.1	473.5	447.9	429.2	416.4	411.7	416.4	429.2	447.9
140°	550.5	515.5	501.5	487.5	463.0	443.2	430.4	426.9	430.4	443.2	463.0
142.5°	561.0	527.2	513.8	500.3	477.0	458.4	446.7	443.2	446.7	458.4	477.0
145°	568.0	537.7	524.8	512.0	489.8	473.5	461.9	458.4	461.9	473.5	489.8
147.5°	576.2	547.0	535.4	523.7	505.0	487.5	477.0	475.8	477.0	487.5	505.0
150°	582.0	556.3	545.2	534.2	516.7	502.7	493.3	492.2	493.3	502.7	516.7
152.5°	586.6	564.5	554.6	544.7	529.5	516.7	507.3	507.3	507.3	516.7	529.5
155°	591.3	571.5	562.8	554.0	541.2	529.5	522.5	521.3	522.5	529.5	541.2
157.5°	594.8	577.3	570.3	563.3	551.7	542.3	535.3	535.3	535.3	542.3	551.7
160°	597.1	583.1	576.7	570.3	561.0	552.8	548.2	548.2	548.2	552.8	561.0
162.5°	599.5	586.6	582.0	577.3	569.2	562.2	558.7	559.8	558.7	562.2	569.2
165°	599.5	589.0	585.5	582.0	576.2	570.3	568.0	568.0	568.0	570.3	576.2
167.5°	599.5	591.3	588.4	585.5	582.0	577.3	576.2	577.3	576.2	577.3	582.0
170°	598.3	592.5	590.8	589.0	586.6	583.1	582.0	583.1	582.0	583.1	586.6
172.5°	597.1	593.6	592.4	591.3	590.1	587.8	587.8	589.0	587.8	587.8	590.1
175°	596.0	593.6	593.6	593.6	592.5	591.3	591.3	592.5	591.3	591.3	592.5
177.5°	594.8	593.6	593.6	593.6	593.6	592.5	593.6	594.8	593.6	592.5	593.6
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1311.3	1309.1	1307.0	1298.4	1290.9	1278.0	1267.2	1262.9	1261.9	1262.9	1259.7
5°	1273.7	1272.6	1265.1	1250.0	1236.1	1221.0	1210.3	1199.6	1193.1	1193.1	1185.6
7.5°	1238.2	1230.7	1224.3	1204.9	1188.8	1168.4	1152.3	1142.7	1137.3	1125.5	1125.5
10°	1200.6	1189.9	1181.3	1163.1	1139.4	1119.0	1098.6	1086.8	1077.1	1068.6	1065.3
12.5°	1163.1	1154.5	1138.4	1119.0	1095.4	1069.6	1048.1	1039.6	1017.0	998.7	999.8
15°	1127.6	1108.3	1100.8	1072.8	1044.9	1020.2	989.1	964.4	946.1	934.3	919.3
17.5°	1087.9	1068.6	1054.6	1031.0	994.5	955.8	925.7	892.4	874.2	853.8	844.1
20°	1043.9	1027.7	1017.0	979.4	935.4	889.2	855.9	835.5	815.1	800.1	791.5
22.5°	1006.3	985.9	973.0	922.5	874.2	828.0	802.2	785.0	767.9	755.0	750.7
25°	957.9	946.1	915.0	870.9	811.9	780.7	758.2	735.6	726.0	717.4	707.7
27.5°	918.2	889.2	867.7	809.7	773.2	737.8	715.2	698.0	686.2	677.6	670.1
30°	868.8	842.0	811.9	763.6	730.3	697.0	676.6	662.6	649.7	644.4	637.9
32.5°	817.3	792.6	763.6	724.9	684.1	658.3	642.2	627.2	618.6	613.2	605.7
35°	771.1	739.9	720.6	684.1	650.8	621.8	606.8	593.9	584.2	582.1	581.0
37.5°	721.7	698.0	679.8	642.2	614.3	589.6	575.6	561.7	556.3	555.2	550.9
40°	678.7	658.3	641.1	605.7	575.6	553.1	542.3	533.7	528.4	528.4	527.3
42.5°	641.1	619.7	602.5	570.3	543.4	523.0	511.2	502.6	500.4	501.5	500.4
45°	599.2	581.0	563.8	530.5	508.0	492.9	480.0	475.7	472.5	473.6	474.7
47.5°	559.5	544.5	527.3	500.4	474.7	458.6	451.0	446.8	446.8	446.8	448.9
50°	524.1	506.9	491.9	463.9	440.3	427.4	421.0	415.6	416.7	417.8	418.8
52.5°	482.2	467.2	456.4	428.5	411.3	395.2	387.7	388.8	387.7	387.7	389.8
55°	445.7	430.6	419.9	394.1	376.9	366.2	359.8	356.5	357.6	355.5	359.8
57.5°	404.9	392.0	384.5	359.8	344.7	335.1	329.7	324.3	326.5	325.4	324.3
60°	369.4	354.4	342.6	325.4	312.5	300.7	297.5	292.1	294.3	292.1	291.0
62.5°	328.6	316.8	308.2	291.0	280.3	270.6	263.1	259.9	258.8	255.6	252.4
65°	287.8	281.4	272.8	255.6	244.9	237.3	233.0	229.8	228.7	220.2	210.5
67.5°	250.2	245.9	237.3	224.4	214.8	207.3	200.8	195.5	189.0	182.6	177.2
70°	214.8	208.3	203.0	191.2	182.6	175.0	168.6	162.2	158.9	152.5	150.3
72.5°	180.4	174.0	168.6	157.9	150.3	142.8	140.7	133.2	129.9	128.9	128.9
75°	145.0	139.6	136.4	126.7	120.3	114.9	111.7	109.5	107.4	105.2	102.0
77.5°	110.6	107.4	105.2	98.8	93.4	90.2	89.1	81.6	79.5	77.3	75.2
80°	80.5	79.5	77.3	72.0	69.8	62.3	62.3	60.1	59.1	59.1	59.1
82.5°	54.8	52.6	51.5	46.2	45.1	44.0	43.0	41.9	43.0	41.9	43.0
85°	29.0	27.9	26.8	26.8	26.8	26.8	26.8	26.8	26.8	25.8	26.8
87.5°	10.7	10.7	10.7	10.7	9.7	10.7	10.7	9.7	10.7	10.7	10.7
90°	9.3	9.3	9.3	16.3	16.3	18.7	21.0	19.8	21.0	22.2	23.3
92.5°	74.6	89.8	105.0	177.3	290.4	400.0	457.2	380.2	281.1	209.9	165.6
95°	96.8	121.3	145.8	247.3	438.5	717.3	950.5	977.4	864.2	683.4	527.2
97.5°	113.1	134.1	155.1	235.6	400.0	686.9	1017.0	1225.8	1244.4	1154.6	1026.3
100°	133.0	151.6	170.3	239.1	370.9	608.8	937.7	1236.3	1406.6	1429.9	1372.7
102.5°	155.1	172.6	190.1	250.8	362.7	556.3	838.6	1148.8	1398.4	1537.2	1572.2
105°	180.8	197.7	214.6	270.6	367.4	530.7	765.1	1039.2	1306.3	1508.0	1623.5
107.5°	206.4	223.4	240.3	291.6	381.4	523.7	717.3	949.4	1193.1	1411.2	1572.2
110°	233.3	249.0	264.7	316.1	397.7	526.0	695.1	885.2	1092.8	1294.6	1463.7

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	258.9	274.6	290.4	339.4	415.2	533.0	684.6	849.1	1019.3	1192.0	1349.4
115°	285.7	301.4	317.2	363.9	433.9	542.3	682.3	829.2	975.0	1118.5	1254.9
117.5°	310.2	326.5	342.9	387.2	452.5	551.7	681.1	818.7	949.4	1070.7	1181.5
120°	334.7	351.0	367.4	411.7	472.3	562.2	681.1	810.6	933.0	1041.5	1134.8
122.5°	359.2	375.0	390.7	435.0	491.0	572.7	680.0	801.2	919.0	1022.8	1105.6
125°	381.4	397.7	414.0	456.0	509.7	583.1	678.8	790.7	902.7	1003.0	1083.5
127.5°	402.4	418.7	435.0	475.8	526.0	591.3	676.5	776.8	884.1	980.9	1061.3
130°	422.2	439.1	456.0	495.7	541.2	600.6	675.3	763.9	860.7	952.9	1032.2
132.5°	440.9	456.6	472.3	512.0	556.3	608.8	674.1	752.3	836.2	921.4	998.3
135°	458.4	473.6	488.7	527.2	569.2	617.0	673.0	740.6	814.1	889.9	961.0
137.5°	473.5	488.1	502.7	538.8	578.5	621.6	673.0	730.1	793.1	859.6	921.4
140°	487.5	501.5	515.5	550.5	587.8	627.5	671.8	721.9	775.6	830.4	882.9
142.5°	500.3	513.8	527.2	561.0	594.8	632.1	671.8	714.9	759.3	805.9	849.1
145°	512.0	524.8	537.7	568.0	599.5	633.3	669.5	706.8	744.1	783.8	818.7
147.5°	523.7	535.4	547.0	576.2	604.1	634.5	666.0	699.8	731.3	763.9	793.1
150°	534.2	545.2	556.3	582.0	607.6	634.5	662.5	691.6	719.6	746.4	769.8
152.5°	544.7	554.6	564.5	586.6	610.0	632.1	656.6	682.3	706.8	728.9	749.9
155°	554.0	562.8	571.5	591.3	611.1	629.8	650.8	673.0	693.9	712.6	730.1
157.5°	563.3	570.3	577.3	594.8	611.1	627.5	645.0	663.6	680.0	696.3	711.4
160°	570.3	576.7	583.1	597.1	611.1	624.0	638.0	653.1	667.1	680.0	692.8
162.5°	577.3	582.0	586.6	599.5	611.1	620.5	631.0	643.8	654.3	664.8	674.1
165°	582.0	585.5	589.0	599.5	608.8	615.8	624.0	633.3	642.6	649.6	657.8
167.5°	585.5	588.4	591.3	599.5	606.5	611.1	617.0	624.0	631.0	636.8	643.8
170°	589.0	590.8	592.5	598.3	604.1	606.5	610.0	614.6	620.5	624.0	628.6
172.5°	591.3	592.4	593.6	597.1	601.8	601.8	603.0	606.5	611.1	613.5	615.8
175°	593.6	593.6	593.6	596.0	599.5	598.3	598.3	600.6	603.0	604.1	606.5
177.5°	593.6	593.6	593.6	594.8	597.1	594.8	594.8	596.0	597.1	598.3	598.3
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1259.7	1264.0	1258.6	1261.9	1254.3	1253.3	1254.3	1254.3	1255.4	1256.5	1257.6
5°	1188.8	1187.8	1181.3	1177.0	1173.8	1177.0	1179.2	1181.3	1179.2	1181.3	1182.4
7.5°	1122.2	1119.0	1115.8	1108.3	1110.4	1108.3	1114.7	1111.5	1111.5	1116.9	1121.2
10°	1063.2	1056.7	1054.6	1046.0	1039.6	1038.5	1046.0	1049.2	1052.4	1054.6	1063.2
12.5°	986.9	977.3	969.8	973.0	954.7	962.2	964.4	960.1	973.0	988.0	979.4
15°	905.3	906.4	891.4	886.0	870.9	875.2	876.3	887.1	897.8	896.7	909.6
17.5°	845.2	838.7	825.8	824.8	818.3	821.5	820.5	829.1	825.8	831.2	842.0
20°	789.3	785.0	774.3	770.0	772.1	770.0	771.1	772.1	775.4	787.2	785.0
22.5°	745.3	739.9	739.9	734.6	728.1	726.0	731.3	734.6	738.9	741.0	746.4
25°	706.6	702.3	697.0	693.8	688.4	689.5	692.7	697.0	700.2	704.5	708.8
27.5°	666.9	666.9	661.5	660.5	658.3	657.2	661.5	663.7	663.7	666.9	671.2
30°	635.8	635.8	630.4	629.3	628.2	628.2	631.5	632.5	633.6	636.8	639.0
32.5°	605.7	604.6	602.5	603.5	602.5	603.5	603.5	604.6	606.8	607.8	612.1
35°	577.8	578.8	576.7	576.7	575.6	576.7	578.8	579.9	581.0	583.1	583.1
37.5°	550.9	553.1	552.0	555.2	555.2	555.2	555.2	557.4	557.4	557.4	556.3
40°	527.3	527.3	526.2	528.4	530.5	530.5	531.6	531.6	532.7	532.7	531.6
42.5°	500.4	502.6	505.8	506.9	509.0	508.0	511.2	510.1	511.2	509.0	506.9
45°	475.7	475.7	480.0	484.3	485.4	485.4	485.4	487.6	485.4	482.2	481.1
47.5°	448.9	451.0	453.2	458.6	459.6	459.6	459.6	459.6	457.5	457.5	457.5
50°	422.1	423.1	424.2	426.3	429.6	428.5	428.5	428.5	432.8	428.5	429.6
52.5°	389.8	390.9	392.0	396.3	395.2	395.2	396.3	396.3	399.5	398.4	396.3
55°	357.6	357.6	359.8	359.8	359.8	361.9	363.0	365.1	364.1	365.1	366.2
57.5°	325.4	323.3	322.2	322.2	325.4	324.3	325.4	325.4	329.7	331.8	332.9
60°	287.8	287.8	286.7	280.3	280.3	279.2	282.4	284.6	286.7	296.4	295.3
62.5°	249.1	244.9	240.6	241.6	235.2	238.4	236.3	238.4	244.9	252.4	253.4
65°	210.5	207.3	203.0	201.9	199.7	203.0	201.9	203.0	206.2	210.5	215.9
67.5°	176.1	175.0	172.9	171.8	171.8	171.8	174.0	174.0	175.0	178.3	181.5
70°	150.3	149.3	150.3	148.2	149.3	148.2	149.3	150.3	151.4	152.5	155.7
72.5°	126.7	126.7	126.7	124.6	126.7	125.6	125.6	126.7	127.8	128.9	131.0
75°	100.9	98.8	96.7	94.5	93.4	95.6	96.7	95.6	98.8	103.1	103.1
77.5°	76.2	75.2	75.2	75.2	76.2	75.2	77.3	76.2	77.3	77.3	79.5
80°	59.1	58.0	59.1	59.1	58.0	60.1	59.1	59.1	60.1	61.2	60.1
82.5°	43.0	44.0	43.0	43.0	43.0	45.1	43.0	43.0	43.0	44.0	44.0
85°	26.8	26.8	26.8	26.8	27.9	26.8	27.9	26.8	29.0	27.9	27.9
87.5°	9.7	10.7	11.8	11.8	11.8	11.8	10.7	11.8	12.9	11.8	12.9
90°	23.3	23.3	24.5	25.7	24.5	24.5	24.5	25.7	24.5	23.3	23.3
92.5°	151.0	136.5	119.0	110.8	106.1	106.1	106.1	110.8	119.0	136.5	151.0
95°	470.6	414.0	356.9	320.7	299.7	284.6	299.7	320.7	356.9	414.0	470.6
97.5°	961.0	895.7	816.4	746.4	711.4	683.4	711.4	746.4	816.4	895.7	961.0
100°	1329.6	1286.4	1185.0	1113.8	1078.8	1069.5	1078.8	1113.8	1185.0	1286.4	1329.6
102.5°	1560.5	1548.8	1496.4	1449.7	1412.4	1405.4	1412.4	1449.7	1496.4	1548.8	1560.5
105°	1647.4	1671.3	1673.6	1664.3	1648.0	1641.0	1648.0	1664.3	1673.6	1671.3	1647.4
107.5°	1621.2	1670.1	1721.5	1742.4	1751.8	1752.9	1751.8	1742.4	1721.5	1670.1	1621.2
110°	1527.8	1592.0	1674.8	1723.8	1744.8	1755.3	1744.8	1723.8	1674.8	1592.0	1527.8

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1413.6	1477.7	1574.5	1636.3	1667.8	1686.5	1667.8	1636.3	1574.5	1477.7	1413.6
115°	1310.9	1366.9	1459.0	1529.0	1566.3	1575.7	1566.3	1529.0	1459.0	1366.9	1310.9
117.5°	1230.4	1279.4	1361.1	1421.7	1461.4	1467.2	1461.4	1421.7	1361.1	1279.4	1230.4
120°	1176.2	1217.6	1284.1	1335.4	1365.7	1378.6	1365.7	1335.4	1284.1	1217.6	1176.2
122.5°	1140.6	1175.6	1229.3	1271.3	1295.8	1308.6	1295.8	1271.3	1229.3	1175.6	1140.6
125°	1115.6	1147.6	1194.3	1228.1	1250.3	1257.3	1250.3	1228.1	1194.3	1147.6	1115.6
127.5°	1091.6	1122.0	1168.6	1199.0	1217.6	1224.6	1217.6	1199.0	1168.6	1122.0	1091.6
130°	1063.1	1094.0	1141.8	1171.0	1189.6	1196.6	1189.6	1171.0	1141.8	1094.0	1063.1
132.5°	1029.2	1060.2	1106.8	1140.6	1158.1	1165.1	1158.1	1140.6	1106.8	1060.2	1029.2
135°	990.2	1019.3	1066.0	1098.7	1117.3	1124.3	1117.3	1098.7	1066.0	1019.3	990.2
137.5°	948.2	975.0	1019.3	1053.2	1068.3	1076.5	1068.3	1053.2	1019.3	975.0	948.2
140°	907.4	931.9	972.7	998.3	1014.7	1024.0	1014.7	998.3	972.7	931.9	907.4
142.5°	869.5	889.9	924.9	948.2	962.2	968.0	962.2	948.2	924.9	889.9	869.5
145°	835.0	851.4	880.6	900.4	912.0	917.9	912.0	900.4	880.6	851.4	835.0
147.5°	806.5	819.9	842.1	859.6	868.9	871.2	868.9	859.6	842.1	819.9	806.5
150°	780.2	790.7	809.4	824.6	831.6	832.7	831.6	824.6	809.4	790.7	780.2
152.5°	758.1	766.3	781.4	793.1	796.6	797.7	796.6	793.1	781.4	766.3	758.1
155°	737.1	744.1	755.8	765.1	768.6	768.6	768.6	765.1	755.8	744.1	737.1
157.5°	717.2	723.1	732.4	739.4	741.8	741.8	741.8	739.4	732.4	723.1	717.2
160°	697.4	702.1	709.1	716.1	717.3	717.3	717.3	716.1	709.1	702.1	697.4
162.5°	678.2	682.3	686.9	693.9	695.1	693.9	695.1	693.9	686.9	682.3	678.2
165°	660.7	663.6	668.3	673.0	671.8	670.6	671.8	673.0	668.3	663.6	660.7
167.5°	645.6	647.3	649.6	653.1	653.1	652.0	653.1	653.1	649.6	647.3	645.6
170°	630.4	632.1	634.5	635.6	634.5	634.5	634.5	635.6	634.5	632.1	630.4
172.5°	617.0	618.1	619.3	620.5	619.3	617.0	619.3	620.5	619.3	618.1	617.0
175°	606.5	606.5	606.5	608.8	606.5	604.1	606.5	608.8	606.5	606.5	606.5
177.5°	598.9	599.5	598.3	599.5	597.1	594.8	597.1	599.5	598.3	599.5	598.9
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1261.9	1267.2	1265.1	1257.6	1260.8	1267.2	1273.7	1282.3	1287.6	1291.9	1294.1
5°	1187.8	1197.4	1195.3	1195.3	1199.6	1210.3	1221.0	1239.3	1245.7	1253.3	1264.0
7.5°	1122.2	1129.8	1136.2	1138.4	1144.8	1158.8	1172.7	1193.1	1209.2	1217.8	1224.3
10°	1064.3	1069.6	1079.3	1084.7	1091.1	1108.3	1128.7	1150.2	1166.3	1181.3	1189.9
12.5°	990.2	1011.6	1024.5	1033.1	1041.7	1067.5	1083.6	1107.2	1126.5	1140.5	1153.4
15°	907.5	933.2	940.8	974.0	995.5	1015.9	1040.6	1068.6	1086.8	1102.9	1120.1
17.5°	837.7	855.9	864.5	899.9	918.2	950.4	985.9	1021.3	1049.2	1061.0	1078.2
20°	793.6	803.3	820.5	832.3	851.6	889.2	927.9	970.8	1012.7	1024.5	1041.7
22.5°	748.5	761.4	773.2	789.3	804.4	830.1	868.8	916.1	961.2	982.6	1003.0
25°	707.7	720.6	728.1	745.3	759.3	785.0	811.9	860.2	913.9	932.2	964.4
27.5°	675.5	683.0	695.9	703.4	719.5	743.2	767.9	804.4	857.0	888.1	919.3
30°	643.3	648.6	659.4	670.1	681.9	698.0	726.0	761.4	809.7	836.6	867.7
32.5°	611.1	619.7	626.1	633.6	646.5	665.8	685.2	719.5	758.2	788.3	819.4
35°	584.2	587.4	596.0	604.6	613.2	630.4	650.8	684.1	718.5	742.1	770.0
37.5°	555.2	560.6	567.0	570.3	584.2	595.0	616.4	642.2	683.0	698.0	726.0
40°	532.7	531.6	538.0	543.4	549.8	567.0	579.9	607.8	640.1	663.7	680.9
42.5°	504.7	504.7	506.9	513.3	521.9	532.7	547.7	571.3	604.6	621.8	642.2
45°	482.2	479.0	480.0	484.3	489.7	500.4	515.5	535.9	569.2	583.1	604.6
47.5°	455.3	452.1	452.1	456.4	460.7	468.2	480.0	503.7	530.5	548.8	564.9
50°	425.3	426.3	425.3	428.5	430.6	438.2	451.0	470.4	495.1	510.1	528.4
52.5°	397.4	395.2	394.1	396.3	400.6	405.9	419.9	437.1	460.7	475.7	491.9
55°	363.0	365.1	365.1	365.1	371.6	373.7	384.5	401.6	425.3	437.1	452.1
57.5°	331.8	330.8	332.9	331.8	337.2	344.7	353.3	366.2	389.8	401.6	415.6
60°	297.5	298.6	299.6	299.6	303.9	311.4	321.1	332.9	352.2	364.1	376.9
62.5°	255.6	261.0	266.3	268.5	274.9	280.3	286.7	299.6	316.8	325.4	337.2
65°	215.9	223.4	230.9	236.3	240.6	245.9	254.5	266.3	280.3	288.9	300.7
67.5°	181.5	186.9	196.5	201.9	210.5	216.9	222.3	232.0	249.1	252.4	262.0
70°	156.8	158.9	163.2	167.5	177.2	182.6	189.0	198.7	211.6	219.1	224.4
72.5°	132.1	133.2	135.3	139.6	143.9	150.3	157.9	166.5	178.3	181.5	189.0
75°	105.2	111.7	111.7	114.9	118.1	121.4	127.8	136.4	143.9	149.3	153.6
77.5°	78.4	81.6	83.8	89.1	93.4	96.7	100.9	107.4	111.7	116.0	119.2
80°	61.2	62.3	63.4	63.4	65.5	69.8	74.1	78.4	83.8	85.9	89.1
82.5°	45.1	45.1	45.1	47.3	48.3	49.4	49.4	51.5	56.9	59.1	62.3
85°	29.0	29.0	29.0	29.0	30.1	31.1	32.2	33.3	33.3	33.3	35.4
87.5°	11.8	14.0	12.9	14.0	14.0	14.0	14.0	15.0	15.0	16.1	16.1
90°	23.3	22.2	21.0	19.8	21.0	18.7	16.3	16.3	9.3	9.3	9.3
92.5°	165.6	209.9	281.1	380.2	457.2	400.0	290.4	177.3	105.0	89.8	74.6
95°	527.2	683.4	864.2	977.4	950.5	717.3	438.5	247.3	145.8	121.3	96.8
97.5°	1026.3	1154.6	1244.4	1225.8	1017.0	686.9	400.0	235.6	155.1	134.1	113.1
100°	1372.7	1429.9	1406.6	1236.3	937.7	608.8	370.9	239.1	170.3	151.6	133.0
102.5°	1572.2	1537.2	1398.4	1148.8	838.6	556.3	362.7	250.8	190.1	172.6	155.1
105°	1623.5	1508.0	1306.3	1039.2	765.1	530.7	367.4	270.6	214.6	197.7	180.8
107.5°	1572.2	1411.2	1193.1	949.4	717.3	523.7	381.4	291.6	240.3	223.4	206.4
110°	1463.7	1294.6	1092.8	885.2	695.1	526.0	397.7	316.1	264.7	249.0	233.3

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1349.4	1192.0	1019.3	849.1	684.6	533.0	415.2	339.4	290.4	274.6	258.9
115°	1254.9	1118.5	975.0	829.2	682.3	542.3	433.9	363.9	317.2	301.4	285.7
117.5°	1181.5	1070.7	949.4	818.7	681.1	551.7	452.5	387.2	342.9	326.5	310.2
120°	1134.8	1041.5	933.0	810.6	681.1	562.2	472.3	411.7	367.4	351.0	334.7
122.5°	1105.6	1022.8	919.0	801.2	680.0	572.7	491.0	435.0	390.7	375.0	359.2
125°	1083.5	1003.0	902.7	790.7	678.8	583.1	509.7	456.0	414.0	397.7	381.4
127.5°	1061.3	980.9	884.1	776.8	676.5	591.3	526.0	475.8	435.0	418.7	402.4
130°	1032.2	952.9	860.7	763.9	675.3	600.6	541.2	495.7	456.0	439.1	422.2
132.5°	998.3	921.4	836.2	752.3	674.1	608.8	556.3	512.0	472.3	456.6	440.9
135°	961.0	889.9	814.1	740.6	673.0	617.0	569.2	527.2	488.7	473.6	458.4
137.5°	921.4	859.6	793.1	730.1	673.0	621.6	578.5	538.8	502.7	488.1	473.5
140°	882.9	830.4	775.6	721.9	671.8	627.5	587.8	550.5	515.5	501.5	487.5
142.5°	849.1	805.9	759.3	714.9	671.8	632.1	594.8	561.0	527.2	513.8	500.3
145°	818.7	783.8	744.1	706.8	669.5	633.3	599.5	568.0	537.7	524.8	512.0
147.5°	793.1	763.9	731.3	699.8	666.0	634.5	604.1	576.2	547.0	535.4	523.7
150°	769.8	746.4	719.6	691.6	662.5	634.5	607.6	582.0	556.3	545.2	534.2
152.5°	749.9	728.9	706.8	682.3	656.6	632.1	610.0	586.6	564.5	554.6	544.7
155°	730.1	712.6	693.9	673.0	650.8	629.8	611.1	591.3	571.5	562.8	554.0
157.5°	711.4	696.3	680.0	663.6	645.0	627.5	611.1	594.8	577.3	570.3	563.3
160°	692.8	680.0	667.1	653.1	638.0	624.0	611.1	597.1	583.1	576.7	570.3
162.5°	674.1	664.8	654.3	643.8	631.0	620.5	611.1	599.5	586.6	582.0	577.3
165°	657.8	649.6	642.6	633.3	624.0	615.8	608.8	599.5	589.0	585.5	582.0
167.5°	643.8	636.8	631.0	624.0	617.0	611.1	606.5	599.5	591.3	588.4	585.5
170°	628.6	624.0	620.5	614.6	610.0	606.5	604.1	598.3	592.5	590.8	589.0
172.5°	615.8	613.5	611.1	606.5	603.0	601.8	601.8	597.1	593.6	592.4	591.3
175°	606.5	604.1	603.0	600.6	598.3	598.3	599.5	596.0	593.6	593.6	593.6
177.5°	598.3	598.3	597.1	596.0	594.8	594.8	597.1	594.8	593.6	593.6	593.6
180°	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6	593.6

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1332.7	1332.7	1332.7	1332.7
2.5°	1302.7	1309.1	1319.8	1334.9
5°	1272.6	1290.9	1308.0	1330.6
7.5°	1245.7	1267.2	1290.9	1323.1
10°	1214.6	1241.5	1271.5	1311.3
12.5°	1178.1	1215.7	1250.0	1293.0
15°	1151.2	1179.2	1223.2	1273.7
17.5°	1113.7	1151.2	1195.3	1252.2
20°	1078.2	1118.0	1167.4	1226.4
22.5°	1040.6	1085.7	1135.1	1198.5
25°	1002.0	1050.3	1099.7	1167.4
27.5°	966.5	1010.6	1066.4	1135.1
30°	923.6	974.0	1027.7	1099.7
32.5°	881.7	934.3	989.1	1061.0
35°	836.6	889.2	949.3	1018.1
37.5°	792.6	850.5	905.3	971.9
40°	744.2	804.4	861.3	928.9
42.5°	697.0	759.3	816.2	874.2
45°	652.9	714.2	765.7	820.5
47.5°	611.1	665.8	718.5	767.9
50°	570.3	616.4	664.8	705.6
52.5°	527.3	571.3	610.0	646.5
55°	488.6	523.0	557.4	590.7
57.5°	442.5	476.8	506.9	532.7
60°	403.8	425.3	454.3	481.1
62.5°	359.8	384.5	407.0	424.2
65°	316.8	338.3	355.5	370.5
67.5°	280.3	293.2	306.1	322.2
70°	236.3	247.0	262.0	273.8
72.5°	198.7	207.3	214.8	228.7
75°	161.1	168.6	172.9	185.8
77.5°	124.6	132.1	135.3	142.8
80°	95.6	96.7	100.9	107.4
82.5°	65.5	67.7	68.7	74.1
85°	37.6	43.0	41.9	44.0
87.5°	16.1	17.2	19.3	21.5
90°	8.2	7.0	3.5	1.2
92.5°	53.6	36.2	23.3	16.3
95°	68.8	53.6	42.0	38.5
97.5°	88.6	74.6	64.1	64.1
100°	110.8	96.8	88.6	88.6
102.5°	134.1	121.3	114.3	112.0
105°	159.8	145.8	140.0	136.5
107.5°	186.6	171.4	165.6	163.3
110°	212.3	198.3	192.4	190.1

TEST NUMBER: P1026573

CATALOG NUMBER: S124RDIP-B795D1205UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	237.9	225.1	218.1	215.8
115°	263.6	251.9	243.8	240.3
117.5°	289.2	276.4	269.4	265.9
120°	314.9	302.1	293.9	291.6
122.5°	337.1	325.4	317.2	314.9
125°	359.2	346.4	339.4	334.7
127.5°	379.0	365.1	356.9	353.4
130°	400.0	382.5	373.2	368.5
132.5°	416.4	400.0	387.2	383.7
135°	433.9	414.0	402.4	397.7
137.5°	447.9	429.2	416.4	411.7
140°	463.0	443.2	430.4	426.9
142.5°	477.0	458.4	446.7	443.2
145°	489.8	473.5	461.9	458.4
147.5°	505.0	487.5	477.0	475.8
150°	516.7	502.7	493.3	492.2
152.5°	529.5	516.7	507.3	507.3
155°	541.2	529.5	522.5	521.3
157.5°	551.7	542.3	535.3	535.3
160°	561.0	552.8	548.2	548.2
162.5°	569.2	562.2	558.7	559.8
165°	576.2	570.3	568.0	568.0
167.5°	582.0	577.3	576.2	577.3
170°	586.6	583.1	582.0	583.1
172.5°	590.1	587.8	587.8	589.0
175°	592.5	591.3	591.3	592.5
177.5°	593.6	592.5	593.6	594.8
180°	593.6	593.6	593.6	593.6

(END OF REPORT)