

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026833

Luminaire Tested: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026833
REPORT IS A COMBINATION OF REPORTS P1001832 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5378.1 lumens
Efficiency: N/A
Efficacy: 129.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35			27
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30			23
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25			19
3	77	68	61	56	69	61	55	50	48	44	40	36	33	31	24	23	21			16
4	70	60	53	47	63	54	48	43	42	38	34	32	29	26	22	20	18			14
5	65	53	46	40	57	48	41	36	38	33	30	28	25	23	20	18	16			12
6	59	48	40	35	53	43	36	32	34	29	26	26	22	20	18	16	14			11
7	55	43	35	30	49	39	32	28	31	26	22	23	20	17	16	14	13			10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11			9
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	14	12	10			8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9			7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3265	3265	3265	3265
5°	3268	3704	3270	2810
10°	3248	4221	3242	2412
15°	3224	4577	3204	2179
20°	3183	5016	3154	1990
25°	3147	5748	3089	1877
30°	3095	6063	3041	1776
35°	3013	4860	2950	1693
40°	2884	3359	2842	1608
45°	2723	2501	2692	1535
50°	2538	2059	2495	1478
55°	2337	1756	2319	1428
60°	2141	1503	2104	1389
65°	1930	1298	1898	1333
70°	1706	1078	1683	1234
75°	1470	834	1449	1072
80°	1160	564	1118	788
85°	743	282	715	401

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 4987 cd/sqm

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	0.9
10°-20°	146.1	2.7
20°-30°	237.3	4.4
30°-40°	290.0	5.4
40°-50°	263.1	4.9
50°-60°	209.5	3.9
60°-70°	145.9	2.7
70°-80°	77.7	1.4
80°-90°	21.2	0.4
90°-100°	43.5	0.8
100°-110°	289.3	5.4
110°-120°	521.0	9.7
120°-130°	668.8	12.4
130°-140°	719.3	13.4
140°-150°	675.1	12.6
150°-160°	546.1	10.2
160°-170°	353.2	6.6
170°-180°	121.8	2.3
0°-30°	432.4	8.0
0°-40°	722.4	13.4
0°-60°	1195.0	22.2
0°-90°	1439.9	26.8
90°-120°	853.9	15.9
90°-150°	2917.1	54.2
90°-180°	3938.0	73.2
0°-180°	5378.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	510	510	510	510	510	
5°	509	588	510	446	509	48
15°	489	734	486	350	489	138
25°	450	903	442	295	450	207
35°	392	725	384	253	392	245
45°	308	342	304	210	308	237
55°	217	211	215	171	217	194
65°	134	129	132	133	134	133
75°	65	64	64	82	65	69
85°	13	14	12	20	13	16
90°	1	23	1	23	1	4
95°	54	20	54	20	54	66
105°	279	282	279	282	279	296
115°	525	521	525	521	525	520
125°	746	746	746	746	746	666
135°	930	927	930	927	930	717
145°	1079	1076	1079	1076	1079	675
155°	1188	1179	1188	1179	1188	547
165°	1254	1247	1254	1247	1254	354
175°	1282	1276	1282	1276	1282	122
180°	1282	1282	1282	1282	1282	

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	510.5	513.5	516.9	519.5	523.9	525.2	527.3	528.6	529.9	531.2	532.1
5°	509.2	516.5	523.0	527.8	536.0	539.0	542.9	547.7	553.3	558.0	561.1
7.5°	505.7	517.4	526.0	535.5	546.8	554.2	558.0	568.0	577.1	584.0	593.1
10°	501.4	515.2	528.6	542.9	558.9	567.1	574.9	588.8	601.3	612.6	621.6
12.5°	496.6	513.5	529.5	548.1	569.7	579.7	584.9	608.7	624.2	630.3	648.0
15°	489.3	509.2	532.1	555.0	573.2	584.9	599.1	618.2	633.7	647.2	661.4
17.5°	482.3	504.0	527.3	552.9	579.2	594.4	605.2	622.1	638.9	656.2	669.7
20°	471.1	499.2	523.0	550.3	581.4	592.2	603.5	623.4	641.5	660.1	677.0
22.5°	462.0	488.8	521.3	547.2	573.6	584.4	598.3	619.0	640.7	661.9	686.5
25°	450.3	480.2	508.3	536.0	563.2	574.9	587.5	614.3	636.8	664.0	691.3
27.5°	437.8	468.5	496.6	521.7	547.2	563.2	576.6	604.8	634.6	664.5	699.9
30°	424.4	453.4	480.2	504.8	533.0	549.4	562.8	595.7	629.0	667.1	709.5
32.5°	410.1	437.4	460.3	485.4	515.2	530.4	548.5	584.4	623.8	669.2	722.4
35°	391.9	417.9	438.2	463.7	493.6	513.1	532.1	572.3	618.2	668.8	729.8
37.5°	373.8	394.1	413.6	440.8	475.4	493.2	513.1	557.2	609.5	667.5	732.8
40°	352.1	372.0	388.9	416.6	452.9	473.3	494.0	540.3	599.6	662.7	722.0
42.5°	330.5	347.4	366.0	395.0	430.0	451.6	473.7	525.2	586.6	648.9	692.1
45°	308.0	321.0	341.3	367.7	404.9	425.7	450.8	506.6	568.4	623.8	645.4
47.5°	284.6	297.6	316.7	342.2	379.0	403.6	427.4	483.2	545.5	588.3	588.3
50°	262.2	272.5	291.1	316.7	353.9	376.4	400.6	459.8	510.0	541.6	513.5
52.5°	237.9	249.6	265.2	292.0	328.8	349.1	375.5	426.1	473.7	486.7	443.4
55°	216.7	226.2	241.0	266.5	300.7	321.8	344.3	392.8	433.0	432.2	385.9
57.5°	194.7	202.5	218.0	241.4	273.0	292.0	314.5	356.5	389.3	377.7	334.0
60°	174.3	180.0	195.1	214.1	244.4	262.2	283.8	318.0	343.0	326.6	282.5
62.5°	153.1	159.6	171.7	190.3	217.2	231.4	247.4	282.1	298.1	283.3	238.4
65°	134.1	139.3	150.1	165.7	189.9	202.9	216.7	245.3	260.4	239.2	202.0
67.5°	115.1	121.1	128.9	142.8	161.8	173.9	186.0	210.7	217.6	198.6	167.4
70°	97.3	102.5	109.9	119.8	135.8	146.6	155.7	176.1	180.8	163.1	138.4
72.5°	80.0	83.5	89.5	97.8	112.5	118.5	128.0	141.9	147.9	131.9	114.2
75°	64.9	67.5	71.4	77.4	87.4	93.9	101.7	114.6	114.2	103.0	90.4
77.5°	50.2	50.6	54.9	60.6	66.6	72.2	76.1	85.2	86.1	79.2	68.8
80°	35.9	37.2	38.9	43.3	48.5	50.6	55.4	61.0	61.9	56.7	49.7
82.5°	22.9	23.8	25.1	27.7	31.1	33.7	36.3	38.5	40.7	37.6	32.0
85°	13.0	13.4	14.7	15.6	17.3	18.6	20.8	22.9	22.5	20.3	18.6
87.5°	6.5	6.5	6.5	7.4	8.2	8.2	9.1	9.5	9.9	9.1	8.2
90°	1.0	2.7	4.4	6.1	7.8	8.6	9.3	10.8	12.3	13.7	15.2
92.5°	18.1	16.2	14.3	12.4	10.5	9.5	10.1	11.4	12.7	13.9	15.2
95°	54.2	53.6	52.9	52.3	51.6	51.3	47.3	39.3	31.2	23.2	15.2
97.5°	101.7	103.0	104.2	105.5	106.8	107.4	97.4	77.3	57.2	37.2	17.1
100°	158.7	159.3	160.0	160.6	161.3	161.6	162.0	162.9	163.7	164.6	165.4
102.5°	216.7	217.5	218.4	219.2	220.1	220.5	220.7	221.1	221.6	222.0	222.4
105°	279.4	280.2	281.1	281.9	282.8	283.2	283.2	283.2	283.2	283.2	283.2
107.5°	344.0	344.0	344.0	344.0	344.0	344.0	344.2	344.6	345.1	345.5	345.9
110°	406.7	406.7	406.7	406.7	406.7	406.7	406.9	407.4	407.8	408.3	408.7

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	465.7	466.3	466.9	467.6	468.2	468.5	468.6	468.8	469.1	469.3	469.5
115°	524.6	525.6	526.7	527.7	528.8	529.3	529.4	529.6	529.9	530.1	530.3
117.5°	586.4	586.4	586.4	586.4	586.4	586.4	586.8	587.7	588.5	589.4	590.2
120°	643.4	643.2	643.0	642.7	642.5	642.4	642.7	643.4	644.0	644.7	645.3
122.5°	693.8	694.8	695.9	696.9	698.0	698.5	698.6	698.8	699.1	699.3	699.5
125°	746.0	747.5	749.0	750.5	752.0	752.7	752.7	752.7	752.7	752.7	752.7
127.5°	796.4	797.4	798.5	799.5	800.6	801.1	801.0	800.8	800.6	800.4	800.2
130°	842.0	843.1	844.1	845.2	846.3	846.8	846.9	847.1	847.3	847.5	847.7
132.5°	887.6	888.9	890.1	891.4	892.7	893.3	893.0	892.4	891.7	891.1	890.5
135°	930.4	931.7	932.9	934.2	935.5	936.1	935.9	935.5	935.0	934.6	934.2
137.5°	970.3	971.6	972.8	974.1	975.4	976.0	975.8	975.4	974.9	974.5	974.1
140°	1009.3	1009.7	1010.1	1010.6	1011.0	1011.2	1011.1	1010.9	1010.6	1010.4	1010.2
142.5°	1044.4	1044.6	1044.8	1045.1	1045.3	1045.4	1045.6	1046.0	1046.5	1046.9	1047.3
145°	1078.6	1079.0	1079.4	1079.9	1080.3	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
147.5°	1109.1	1109.1	1109.1	1109.1	1109.1	1109.1	1109.2	1109.4	1109.6	1109.8	1110.0
150°	1137.6	1137.2	1136.8	1136.3	1135.9	1135.7	1135.9	1136.3	1136.8	1137.2	1137.6
152.5°	1165.1	1164.1	1163.0	1162.0	1160.9	1160.4	1160.6	1161.0	1161.5	1161.9	1162.3
155°	1187.9	1186.6	1185.4	1184.1	1182.8	1182.2	1182.4	1182.8	1183.3	1183.7	1184.1
157.5°	1206.0	1205.4	1204.7	1204.1	1203.4	1203.1	1203.1	1203.1	1203.1	1203.1	1203.1
160°	1225.0	1223.7	1222.5	1221.2	1219.9	1219.3	1219.4	1219.6	1219.8	1220.0	1220.2
162.5°	1240.2	1238.9	1237.7	1236.4	1235.1	1234.5	1234.6	1234.8	1235.1	1235.3	1235.5
165°	1253.5	1252.2	1251.0	1249.7	1248.4	1247.8	1247.9	1248.1	1248.4	1248.6	1248.8
167.5°	1264.0	1262.7	1261.5	1260.2	1258.9	1258.3	1258.4	1258.6	1258.8	1259.0	1259.2
170°	1272.5	1271.0	1269.6	1268.1	1266.6	1265.9	1266.0	1266.2	1266.4	1266.6	1266.8
172.5°	1278.2	1276.7	1275.3	1273.8	1272.3	1271.6	1271.8	1272.2	1272.7	1273.1	1273.5
175°	1282.0	1280.7	1279.5	1278.2	1276.9	1276.3	1276.4	1276.6	1276.9	1277.1	1277.3
177.5°	1284.9	1283.6	1282.4	1281.1	1279.8	1279.2	1279.3	1279.5	1279.7	1279.9	1280.1
180°	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	533.0	536.0	538.6	540.7	542.5	545.1	543.3	543.8	544.6	546.4	546.4
5°	567.6	572.3	574.9	583.6	585.7	585.3	584.0	590.9	590.5	587.9	587.5
7.5°	601.3	609.5	616.9	623.8	626.0	631.6	632.9	635.9	635.0	639.4	637.2
10°	632.0	645.0	651.9	662.3	664.9	667.5	671.0	672.7	676.6	676.1	676.1
12.5°	655.8	671.4	680.5	683.1	693.0	696.0	699.1	704.7	703.4	703.8	706.4
15°	674.4	689.6	697.3	709.5	716.4	719.8	725.0	731.1	730.2	734.1	733.2
17.5°	688.3	702.5	716.8	735.0	735.4	744.5	756.6	759.2	764.8	760.9	760.9
20°	699.5	718.5	738.9	762.2	764.8	770.4	785.2	795.1	801.6	799.4	800.7
22.5°	711.6	738.9	762.7	786.0	798.6	808.5	822.8	838.4	844.0	847.4	846.6
25°	727.2	755.7	790.8	823.2	836.2	855.2	874.3	889.4	893.7	903.3	894.6
27.5°	743.2	783.4	827.1	865.2	881.6	897.2	920.1	931.4	937.0	941.3	938.3
30°	756.6	812.0	859.6	894.6	906.3	915.4	928.3	930.9	928.8	932.2	936.6
32.5°	777.4	831.4	871.7	888.5	887.2	886.8	876.9	863.0	860.0	851.8	863.0
35°	788.6	831.9	847.4	825.0	815.9	799.4	767.9	747.1	728.9	725.0	725.9
37.5°	782.1	799.0	780.4	721.1	706.4	681.3	639.4	610.0	596.5	586.2	599.6
40°	747.1	728.5	677.4	605.2	584.0	560.2	520.8	504.8	485.8	481.9	499.6
42.5°	689.1	632.5	560.2	504.4	482.3	468.9	436.1	420.9	407.5	401.4	411.4
45°	610.4	541.6	468.9	423.1	404.5	388.5	369.0	353.0	344.3	341.7	350.0
47.5°	529.1	456.4	398.4	364.2	344.8	332.7	314.5	305.4	298.5	299.4	300.7
50°	451.2	385.0	340.5	306.3	296.8	287.2	275.1	267.3	263.9	265.2	264.3
52.5°	384.1	330.5	292.9	266.5	262.2	253.1	243.1	236.6	235.3	235.8	237.1
55°	325.3	283.3	253.5	234.5	229.7	223.2	217.2	212.8	209.4	210.7	210.2
57.5°	280.8	244.0	221.1	205.5	202.0	198.1	192.5	190.3	189.0	186.4	188.6
60°	241.4	211.5	191.6	182.1	179.1	176.5	170.4	167.8	167.0	165.7	169.1
62.5°	204.2	183.0	167.8	159.2	156.2	153.6	150.5	148.4	148.8	147.1	148.8
65°	174.8	157.5	146.6	138.9	135.0	133.2	132.8	129.3	128.9	129.3	129.8
67.5°	147.5	132.8	124.6	119.8	116.8	115.1	113.8	111.6	113.3	112.0	112.9
70°	122.9	112.9	104.3	99.5	98.2	98.6	96.5	95.6	96.0	95.2	96.0
72.5°	99.1	90.8	87.4	83.9	82.2	81.8	80.5	79.2	80.5	80.0	80.0
75°	79.2	73.1	69.2	67.1	67.1	66.2	64.0	64.0	64.0	63.6	64.0
77.5°	61.0	55.8	54.1	51.9	51.9	50.6	50.2	50.2	49.3	50.6	49.7
80°	45.4	41.5	38.9	37.6	37.6	37.2	36.3	35.9	36.3	35.9	35.9
82.5°	29.4	27.7	26.4	25.1	24.7	25.1	24.7	23.8	24.2	23.8	24.7
85°	16.9	15.1	15.1	14.3	14.7	13.8	14.3	13.4	13.0	14.3	13.4
87.5°	7.4	6.9	6.9	6.1	6.1	6.1	5.6	6.1	5.6	5.2	5.6
90°	16.3	17.3	18.4	19.5	20.0	20.3	20.9	21.6	22.2	22.8	22.2
92.5°	16.3	17.3	18.4	19.5	20.0	20.1	20.3	20.5	20.7	20.9	20.7
95°	16.3	17.3	18.4	19.5	20.0	20.0	20.0	20.0	20.0	20.0	20.0
97.5°	17.5	17.9	18.4	18.8	19.0	19.1	19.3	19.6	19.8	20.0	19.8
100°	133.9	102.5	71.0	39.5	23.8	23.4	22.5	21.7	20.8	20.0	20.8
102.5°	222.8	223.2	223.7	224.1	224.3	215.4	197.7	180.0	162.2	144.5	162.2
105°	283.2	283.2	283.2	283.2	283.2	283.1	282.9	282.7	282.5	282.3	282.5
107.5°	346.1	346.3	346.6	346.8	346.9	346.5	345.6	344.8	343.9	343.1	343.9
110°	408.1	407.4	406.8	406.1	405.8	405.9	406.1	406.3	406.5	406.7	406.5

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	468.7	467.8	467.0	466.1	465.7	465.5	465.1	464.6	464.2	463.8	464.2
115°	529.5	528.6	527.8	526.9	526.5	525.9	524.6	523.3	522.1	520.8	522.1
117.5°	588.9	587.7	586.4	585.1	584.5	584.3	583.9	583.4	583.0	582.6	583.0
120°	644.9	644.5	644.0	643.6	643.4	642.9	641.8	640.7	639.7	638.6	639.7
122.5°	699.1	698.7	698.2	697.8	697.6	697.0	695.7	694.4	693.2	691.9	693.2
125°	751.9	751.0	750.2	749.3	748.9	748.6	747.9	747.3	746.6	746.0	746.6
127.5°	799.8	799.4	798.9	798.5	798.3	797.5	795.8	794.1	792.4	790.7	792.4
130°	847.1	846.5	845.8	845.2	844.9	844.4	843.3	842.2	841.2	840.1	841.2
132.5°	890.5	890.5	890.5	890.5	890.5	890.0	888.9	887.8	886.8	885.7	886.8
135°	933.8	933.4	932.9	932.5	932.3	931.7	930.4	929.1	927.9	926.6	927.9
137.5°	974.1	974.1	974.1	974.1	974.1	973.6	972.5	971.5	970.4	969.4	970.4
140°	1010.6	1011.0	1011.5	1011.9	1012.1	1011.5	1010.2	1008.9	1007.7	1006.4	1007.7
142.5°	1047.3	1047.3	1047.3	1047.3	1047.3	1046.7	1045.4	1044.1	1042.9	1041.6	1042.9
145°	1080.7	1080.9	1081.2	1081.4	1081.5	1080.9	1079.6	1078.3	1077.1	1075.8	1077.1
147.5°	1110.2	1110.4	1110.7	1110.9	1111.0	1110.3	1108.8	1107.3	1105.8	1104.3	1105.8
150°	1138.0	1138.4	1138.9	1139.3	1139.5	1138.7	1137.0	1135.3	1133.6	1131.9	1133.6
152.5°	1162.7	1163.1	1163.6	1164.0	1164.2	1163.5	1162.0	1160.5	1159.0	1157.5	1159.0
155°	1184.7	1185.4	1186.0	1186.7	1187.0	1186.2	1184.5	1182.8	1181.1	1179.4	1181.1
157.5°	1203.7	1204.4	1205.0	1205.7	1206.0	1205.2	1203.5	1201.8	1200.1	1198.4	1200.1
160°	1221.1	1221.9	1222.8	1223.7	1224.1	1223.2	1221.5	1219.8	1218.1	1216.4	1218.1
162.5°	1236.8	1238.0	1239.3	1240.6	1241.2	1240.2	1238.3	1236.4	1234.5	1232.6	1234.5
165°	1250.1	1251.3	1252.6	1253.9	1254.5	1253.7	1252.0	1250.3	1248.6	1246.9	1248.6
167.5°	1260.7	1262.2	1263.7	1265.2	1265.9	1264.9	1263.0	1261.1	1259.2	1257.3	1259.2
170°	1268.5	1270.2	1271.9	1273.6	1274.4	1273.5	1271.6	1269.7	1267.8	1265.9	1267.8
172.5°	1275.0	1276.4	1277.9	1279.4	1280.1	1279.2	1277.3	1275.4	1273.5	1271.6	1273.5
175°	1279.0	1280.7	1282.4	1284.1	1284.9	1283.9	1282.0	1280.1	1278.2	1276.3	1278.2
177.5°	1281.6	1283.1	1284.6	1286.1	1286.8	1286.0	1284.3	1282.6	1280.9	1279.2	1280.9
180°	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	545.5	542.5	543.3	542.5	540.3	539.0	535.5	531.2	529.5	527.3	526.0
5°	589.2	587.0	586.6	583.1	582.3	577.1	568.4	564.1	558.9	553.7	548.5
7.5°	636.8	634.2	625.5	624.2	625.1	618.6	607.4	598.7	587.9	580.5	570.6
10°	676.1	671.0	663.6	664.0	661.0	652.3	641.1	632.0	616.4	606.9	592.7
12.5°	699.9	695.6	694.7	690.4	687.8	676.6	663.2	651.5	639.8	626.8	616.0
15°	728.9	723.3	719.4	713.3	711.6	699.9	685.2	671.8	658.4	646.3	623.4
17.5°	760.9	754.9	740.2	738.9	728.5	717.2	703.0	683.1	668.8	651.5	634.6
20°	797.3	788.6	769.6	764.8	756.6	738.0	718.5	696.5	673.5	655.8	635.9
22.5°	837.9	822.8	808.9	793.8	787.8	764.8	738.0	711.2	683.5	659.3	635.5
25°	890.7	870.8	851.3	836.2	825.8	796.0	760.1	724.6	692.6	661.0	629.9
27.5°	932.2	914.9	893.7	873.8	860.4	825.0	783.9	738.0	698.2	659.7	626.4
30°	935.3	930.1	917.1	906.3	891.6	853.5	808.1	756.2	706.9	660.1	619.5
32.5°	878.6	889.0	894.6	896.3	893.3	871.2	829.7	772.6	714.6	656.2	613.4
35°	756.6	784.3	818.5	831.4	844.0	855.7	834.0	784.3	717.2	655.4	603.9
37.5°	622.9	648.0	704.7	730.6	745.4	791.6	809.4	782.6	722.4	656.2	594.8
40°	502.7	542.5	583.1	618.2	641.1	693.0	748.0	754.0	715.1	648.0	583.1
42.5°	423.1	446.4	477.1	509.6	529.9	591.4	665.8	709.5	692.1	634.6	568.9
45°	360.3	377.7	406.6	417.5	443.4	502.2	581.0	644.1	652.8	613.4	552.4
47.5°	309.3	324.0	342.6	356.0	376.8	420.9	487.5	557.2	598.7	584.4	529.5
50°	272.5	284.6	300.2	308.0	321.4	361.2	411.4	480.6	536.4	541.2	499.6
52.5°	241.8	248.7	260.9	269.5	280.3	304.5	350.0	407.1	469.8	495.8	462.9
55°	215.0	220.6	231.4	237.1	242.7	263.4	298.9	350.8	409.7	443.8	425.2
57.5°	190.8	195.5	204.6	209.8	212.8	232.7	260.0	300.7	353.4	395.0	384.6
60°	170.9	175.2	180.4	184.3	187.7	204.2	223.2	256.1	303.2	343.5	340.9
62.5°	149.7	153.6	159.2	163.1	166.1	176.5	192.5	217.6	257.8	295.0	302.4
65°	131.1	134.1	138.0	139.7	143.6	151.4	164.4	186.9	219.8	253.1	258.3
67.5°	114.2	115.1	117.7	121.6	122.4	129.3	141.0	157.9	183.4	210.7	218.9
70°	96.0	97.3	99.5	102.5	104.3	108.6	118.5	129.8	151.8	175.6	181.7
72.5°	80.0	81.8	82.6	84.4	85.2	92.1	96.5	107.7	122.9	142.8	149.2
75°	64.9	66.6	67.1	67.9	68.8	71.8	77.9	84.8	97.3	110.3	119.0
77.5°	51.5	51.0	51.9	53.2	52.8	55.4	59.3	65.3	73.5	84.4	90.0
80°	36.3	36.3	37.6	38.9	38.5	41.1	42.4	46.7	53.6	60.6	62.7
82.5°	24.2	24.2	25.5	25.5	26.4	26.8	28.6	30.7	36.3	39.8	41.1
85°	13.8	13.8	14.3	14.3	14.3	15.1	16.4	17.3	19.0	21.2	22.1
87.5°	5.6	6.1	6.1	6.1	6.1	6.9	6.9	7.8	8.2	9.1	9.1
90°	21.6	20.9	20.3	20.0	19.5	18.4	17.3	16.3	15.2	13.7	12.3
92.5°	20.5	20.3	20.1	20.0	19.5	18.4	17.3	16.3	15.2	13.9	12.7
95°	20.0	20.0	20.0	20.0	19.5	18.4	17.3	16.3	15.2	23.2	31.2
97.5°	19.6	19.3	19.1	19.0	18.8	18.4	17.9	17.5	17.1	37.2	57.2
100°	21.7	22.5	23.4	23.8	39.5	71.0	102.5	133.9	165.4	164.6	163.7
102.5°	180.0	197.7	215.4	224.3	224.1	223.7	223.2	222.8	222.4	222.0	221.6
105°	282.7	282.9	283.1	283.2	283.2	283.2	283.2	283.2	283.2	283.2	283.2
107.5°	344.8	345.6	346.5	346.9	346.8	346.6	346.3	346.1	345.9	345.5	345.1
110°	406.3	406.1	405.9	405.8	406.1	406.8	407.4	408.1	408.7	408.3	407.8

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	464.6	465.1	465.5	465.7	466.1	467.0	467.8	468.7	469.5	469.3	469.1
115°	523.3	524.6	525.9	526.5	526.9	527.8	528.6	529.5	530.3	530.1	529.9
117.5°	583.4	583.9	584.3	584.5	585.1	586.4	587.7	588.9	590.2	589.4	588.5
120°	640.7	641.8	642.9	643.4	643.6	644.0	644.5	644.9	645.3	644.7	644.0
122.5°	694.4	695.7	697.0	697.6	697.8	698.2	698.7	699.1	699.5	699.3	699.1
125°	747.3	747.9	748.6	748.9	749.3	750.2	751.0	751.9	752.7	752.7	752.7
127.5°	794.1	795.8	797.5	798.3	798.5	798.9	799.4	799.8	800.2	800.4	800.6
130°	842.2	843.3	844.4	844.9	845.2	845.8	846.5	847.1	847.7	847.5	847.3
132.5°	887.8	888.9	890.0	890.5	890.5	890.5	890.5	890.5	890.5	891.1	891.7
135°	929.1	930.4	931.7	932.3	932.5	932.9	933.4	933.8	934.2	934.6	935.0
137.5°	971.5	972.5	973.6	974.1	974.1	974.1	974.1	974.1	974.1	974.5	974.9
140°	1008.9	1010.2	1011.5	1012.1	1011.9	1011.5	1011.0	1010.6	1010.2	1010.4	1010.6
142.5°	1044.1	1045.4	1046.7	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1046.9	1046.5
145°	1078.3	1079.6	1080.9	1081.5	1081.4	1081.2	1080.9	1080.7	1080.5	1080.5	1080.5
147.5°	1107.3	1108.8	1110.3	1111.0	1110.9	1110.7	1110.4	1110.2	1110.0	1109.8	1109.6
150°	1135.3	1137.0	1138.7	1139.5	1139.3	1138.9	1138.4	1138.0	1137.6	1137.2	1136.8
152.5°	1160.5	1162.0	1163.5	1164.2	1164.0	1163.6	1163.1	1162.7	1162.3	1161.9	1161.5
155°	1182.8	1184.5	1186.2	1187.0	1186.7	1186.0	1185.4	1184.7	1184.1	1183.7	1183.3
157.5°	1201.8	1203.5	1205.2	1206.0	1205.7	1205.0	1204.4	1203.7	1203.1	1203.1	1203.1
160°	1219.8	1221.5	1223.2	1224.1	1223.7	1222.8	1221.9	1221.1	1220.2	1220.0	1219.8
162.5°	1236.4	1238.3	1240.2	1241.2	1240.6	1239.3	1238.0	1236.8	1235.5	1235.3	1235.1
165°	1250.3	1252.0	1253.7	1254.5	1253.9	1252.6	1251.3	1250.1	1248.8	1248.6	1248.4
167.5°	1261.1	1263.0	1264.9	1265.9	1265.2	1263.7	1262.2	1260.7	1259.2	1259.0	1258.8
170°	1269.7	1271.6	1273.5	1274.4	1273.6	1271.9	1270.2	1268.5	1266.8	1266.6	1266.4
172.5°	1275.4	1277.3	1279.2	1280.1	1279.4	1277.9	1276.4	1275.0	1273.5	1273.1	1272.7
175°	1280.1	1282.0	1283.9	1284.9	1284.1	1282.4	1280.7	1279.0	1277.3	1277.1	1276.9
177.5°	1282.6	1284.3	1286.0	1286.8	1286.1	1284.6	1283.1	1281.6	1280.1	1279.9	1279.7
180°	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	524.3	522.1	519.5	519.5	516.5	515.2	512.6	511.8	509.6	506.1	503.5
5°	542.9	537.3	533.8	530.8	524.3	519.5	514.8	509.6	504.4	498.3	491.4
7.5°	561.1	550.7	545.9	540.7	531.2	521.3	511.8	504.8	497.9	488.4	479.7
10°	580.1	567.1	558.5	551.6	536.8	524.3	510.5	500.5	489.7	477.6	466.3
12.5°	596.1	579.2	571.9	558.9	542.0	526.9	509.6	494.5	480.2	465.9	452.1
15°	609.5	593.5	575.3	570.2	546.8	525.2	505.7	486.2	468.5	454.2	438.2
17.5°	613.8	593.5	584.4	571.9	544.2	521.7	497.0	475.9	459.0	437.8	425.2
20°	615.1	595.7	583.1	571.5	546.8	516.9	492.7	466.8	446.4	425.2	405.3
22.5°	611.7	588.8	576.6	565.4	537.7	512.2	484.1	455.5	431.7	412.3	392.4
25°	605.2	578.4	566.7	554.6	528.2	500.1	469.4	442.1	420.0	396.7	377.2
27.5°	596.5	565.8	552.4	539.9	513.9	487.5	458.5	430.4	405.8	381.1	362.9
30°	585.7	550.3	538.1	521.7	496.6	471.5	445.1	417.0	389.3	366.0	346.1
32.5°	571.9	534.7	518.7	503.1	475.9	452.9	427.8	401.4	374.6	351.7	330.9
35°	559.3	516.9	499.2	483.6	453.4	429.1	408.4	383.7	359.9	336.1	317.5
37.5°	542.5	499.2	478.0	462.0	431.3	406.6	387.2	368.1	343.0	320.1	302.8
40°	524.7	477.1	457.3	441.2	409.2	382.4	363.8	346.9	326.6	305.4	287.2
42.5°	508.7	456.0	434.8	415.3	382.8	359.1	340.0	327.0	308.4	289.4	273.0
45°	488.4	433.5	410.5	390.2	359.1	333.1	314.9	304.5	290.7	272.1	257.8
47.5°	467.6	409.2	385.4	365.5	331.8	308.9	291.1	281.2	271.7	257.0	242.7
50°	440.4	383.7	362.1	339.2	305.8	282.5	267.8	257.8	250.5	240.1	228.0
52.5°	410.5	357.3	334.0	314.1	281.2	260.0	243.1	237.5	230.1	222.4	212.0
55°	379.0	328.8	306.3	286.8	256.5	234.9	221.1	215.0	209.4	203.3	196.4
57.5°	347.4	298.9	277.7	260.4	232.3	211.5	200.3	192.1	188.2	184.7	179.1
60°	308.0	266.9	250.5	234.9	207.2	188.2	177.4	171.3	167.8	166.1	163.5
62.5°	273.4	239.7	221.5	206.3	184.3	167.4	157.0	152.3	149.2	148.4	145.4
65°	236.6	207.6	193.4	180.4	161.4	146.2	137.6	131.9	129.8	129.3	129.3
67.5°	202.0	178.7	164.4	155.3	138.9	125.5	117.2	115.1	113.8	112.0	111.6
70°	169.6	151.0	138.4	130.6	115.9	106.0	99.5	96.0	96.0	94.7	93.9
72.5°	141.0	122.4	114.2	107.7	95.6	87.0	82.2	81.3	78.3	77.9	77.9
75°	110.3	96.5	90.8	85.2	76.1	70.1	66.2	64.0	62.3	62.3	62.7
77.5°	83.1	73.5	68.3	64.0	57.5	53.6	50.6	49.7	48.0	48.0	48.0
80°	58.8	53.6	49.7	46.3	41.5	38.1	36.3	34.6	34.6	34.2	34.6
82.5°	38.1	33.7	31.6	31.1	26.8	25.5	23.4	23.8	22.5	22.1	22.9
85°	22.1	19.9	17.3	16.4	14.7	13.0	12.1	12.5	12.1	11.7	12.1
87.5°	8.7	7.4	6.9	6.9	5.6	5.2	4.8	5.2	4.3	4.3	4.8
90°	10.8	9.3	8.6	7.8	6.1	4.4	2.7	1.0	2.7	4.4	6.1
92.5°	11.4	10.1	9.5	10.5	12.4	14.3	16.2	18.1	16.2	14.3	12.4
95°	39.3	47.3	51.3	51.6	52.3	52.9	53.6	54.2	53.6	52.9	52.3
97.5°	77.3	97.4	107.4	106.8	105.5	104.2	103.0	101.7	103.0	104.2	105.5
100°	162.9	162.0	161.6	161.3	160.6	160.0	159.3	158.7	159.3	160.0	160.6
102.5°	221.1	220.7	220.5	220.1	219.2	218.4	217.5	216.7	217.5	218.4	219.2
105°	283.2	283.2	283.2	282.8	281.9	281.1	280.2	279.4	280.2	281.1	281.9
107.5°	344.6	344.2	344.0	344.0	344.0	344.0	344.0	344.0	344.0	344.0	344.0
110°	407.4	406.9	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	468.8	468.6	468.5	468.2	467.6	466.9	466.3	465.7	466.3	466.9	467.6
115°	529.6	529.4	529.3	528.8	527.7	526.7	525.6	524.6	525.6	526.7	527.7
117.5°	587.7	586.8	586.4	586.4	586.4	586.4	586.4	586.4	586.4	586.4	586.4
120°	643.4	642.7	642.4	642.5	642.7	643.0	643.2	643.4	643.2	643.0	642.7
122.5°	698.8	698.6	698.5	698.0	696.9	695.9	694.8	693.8	694.8	695.9	696.9
125°	752.7	752.7	752.7	752.0	750.5	749.0	747.5	746.0	747.5	749.0	750.5
127.5°	800.8	801.0	801.1	800.6	799.5	798.5	797.4	796.4	797.4	798.5	799.5
130°	847.1	846.9	846.8	846.3	845.2	844.1	843.1	842.0	843.1	844.1	845.2
132.5°	892.4	893.0	893.3	892.7	891.4	890.1	888.9	887.6	888.9	890.1	891.4
135°	935.5	935.9	936.1	935.5	934.2	932.9	931.7	930.4	931.7	932.9	934.2
137.5°	975.4	975.8	976.0	975.4	974.1	972.8	971.6	970.3	971.6	972.8	974.1
140°	1010.9	1011.1	1011.2	1011.0	1010.6	1010.1	1009.7	1009.3	1009.7	1010.1	1010.6
142.5°	1046.0	1045.6	1045.4	1045.3	1045.1	1044.8	1044.6	1044.4	1044.6	1044.8	1045.1
145°	1080.5	1080.5	1080.5	1080.3	1079.9	1079.4	1079.0	1078.6	1079.0	1079.4	1079.9
147.5°	1109.4	1109.2	1109.1	1109.1	1109.1	1109.1	1109.1	1109.1	1109.1	1109.1	1109.1
150°	1136.3	1135.9	1135.7	1135.9	1136.3	1136.8	1137.2	1137.6	1137.2	1136.8	1136.3
152.5°	1161.0	1160.6	1160.4	1160.9	1162.0	1163.0	1164.1	1165.1	1164.1	1163.0	1162.0
155°	1182.8	1182.4	1182.2	1182.8	1184.1	1185.4	1186.6	1187.9	1186.6	1185.4	1184.1
157.5°	1203.1	1203.1	1203.1	1203.4	1204.1	1204.7	1205.4	1206.0	1205.4	1204.7	1204.1
160°	1219.6	1219.4	1219.3	1219.9	1221.2	1222.5	1223.7	1225.0	1223.7	1222.5	1221.2
162.5°	1234.8	1234.6	1234.5	1235.1	1236.4	1237.7	1238.9	1240.2	1238.9	1237.7	1236.4
165°	1248.1	1247.9	1247.8	1248.4	1249.7	1251.0	1252.2	1253.5	1252.2	1251.0	1249.7
167.5°	1258.6	1258.4	1258.3	1258.9	1260.2	1261.5	1262.7	1264.0	1262.7	1261.5	1260.2
170°	1266.2	1266.0	1265.9	1266.6	1268.1	1269.6	1271.0	1272.5	1271.0	1269.6	1268.1
172.5°	1272.2	1271.8	1271.6	1272.3	1273.8	1275.3	1276.7	1278.2	1276.7	1275.3	1273.8
175°	1276.6	1276.4	1276.3	1276.9	1278.2	1279.5	1280.7	1282.0	1280.7	1279.5	1278.2
177.5°	1279.5	1279.3	1279.2	1279.8	1281.1	1282.4	1283.6	1284.9	1283.6	1282.4	1281.1
180°	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	502.7	501.8	499.6	498.3	494.0	488.8	487.1	482.8	484.5	481.5	481.5
5°	489.3	485.4	482.8	478.9	470.7	465.0	459.0	456.0	454.2	452.1	450.3
7.5°	472.0	468.9	466.3	459.0	449.9	442.1	434.8	431.7	426.1	422.2	420.5
10°	456.8	452.5	446.4	437.8	428.3	418.3	411.8	405.3	401.0	398.9	394.1
12.5°	441.2	436.1	429.6	417.0	406.6	400.6	388.9	382.8	380.7	379.0	373.3
15°	425.2	419.6	411.8	400.1	391.1	376.8	369.9	365.1	359.9	359.5	355.2
17.5°	411.0	404.0	397.6	383.3	372.0	359.5	355.6	350.4	345.6	340.5	338.3
20°	392.8	386.3	381.5	366.0	353.4	345.6	339.2	334.8	331.8	326.6	325.7
22.5°	376.4	369.4	362.9	351.3	340.5	330.5	322.7	318.0	316.7	314.5	310.6
25°	360.3	353.4	345.6	334.8	323.6	316.7	309.7	306.7	304.1	300.7	297.6
27.5°	346.9	340.5	333.1	319.7	310.2	305.0	297.6	294.2	290.7	289.0	287.7
30°	330.9	323.6	318.0	307.6	297.2	290.3	285.1	282.1	279.0	277.3	276.4
32.5°	315.4	308.4	304.5	293.3	285.1	276.9	273.0	270.8	269.1	267.3	265.6
35°	302.8	295.9	289.8	279.5	271.2	265.6	262.6	259.1	257.8	256.1	256.1
37.5°	287.2	282.1	276.0	266.0	258.7	254.4	251.8	247.4	247.0	246.1	244.8
40°	273.8	268.6	263.0	254.4	247.9	242.7	239.2	237.1	235.8	234.9	234.0
42.5°	259.6	253.9	251.3	241.4	235.8	230.6	228.8	226.7	226.2	224.5	222.4
45°	245.7	241.0	235.8	228.4	223.7	219.3	216.7	215.0	212.8	212.4	211.1
47.5°	233.6	228.0	223.2	216.3	211.1	207.6	205.5	203.3	201.6	200.3	199.0
50°	218.0	213.7	209.8	202.5	198.1	194.7	191.6	189.9	188.2	188.2	188.2
52.5°	202.9	199.0	195.5	190.3	185.1	182.1	178.7	177.4	176.5	175.2	176.5
55°	188.2	184.3	180.8	176.9	170.9	168.3	164.8	163.5	164.0	164.0	165.3
57.5°	172.6	169.6	167.4	162.7	157.0	154.4	152.3	151.0	151.0	152.7	153.1
60°	157.5	154.4	150.5	146.2	142.8	139.7	138.4	138.9	138.9	139.7	141.9
62.5°	140.6	138.9	136.7	130.6	128.5	126.3	124.6	125.9	125.5	127.6	130.6
65°	125.0	123.3	120.3	117.2	114.6	112.5	112.0	112.5	113.3	115.5	119.0
67.5°	107.7	107.7	105.1	102.5	100.4	98.2	98.6	99.1	99.9	102.5	107.7
70°	93.4	91.7	89.1	87.4	85.7	84.8	83.9	85.7	88.2	90.0	93.9
72.5°	77.9	76.6	74.4	72.7	72.2	71.4	70.9	71.8	74.4	77.4	81.8
75°	61.4	61.9	60.6	59.3	59.3	58.0	58.8	58.8	61.4	64.5	67.9
77.5°	47.6	47.2	46.7	45.9	45.4	45.4	45.4	46.3	48.9	50.6	54.1
80°	33.7	34.2	32.9	33.3	32.9	33.3	33.3	35.0	36.3	38.5	41.1
82.5°	22.5	22.5	21.6	22.1	22.1	22.1	22.5	23.4	25.1	26.8	28.6
85°	12.5	13.0	12.1	13.0	13.0	13.0	13.4	13.8	15.1	15.6	17.3
87.5°	4.8	5.6	5.6	4.8	5.2	5.6	6.1	5.6	6.5	7.4	7.8
90°	7.8	8.6	9.3	10.8	12.3	13.7	15.2	16.3	17.3	18.4	19.5
92.5°	10.5	9.5	10.1	11.4	12.7	13.9	15.2	16.3	17.3	18.4	19.5
95°	51.6	51.3	47.3	39.3	31.2	23.2	15.2	16.3	17.3	18.4	19.5
97.5°	106.8	107.4	97.4	77.3	57.2	37.2	17.1	17.5	17.9	18.4	18.8
100°	161.3	161.6	162.0	162.9	163.7	164.6	165.4	133.9	102.5	71.0	39.5
102.5°	220.1	220.5	220.7	221.1	221.6	222.0	222.4	222.8	223.2	223.7	224.1
105°	282.8	283.2	283.2	283.2	283.2	283.2	283.2	283.2	283.2	283.2	283.2
107.5°	344.0	344.0	344.2	344.6	345.1	345.5	345.9	346.1	346.3	346.6	346.8
110°	406.7	406.7	406.9	407.4	407.8	408.3	408.7	408.1	407.4	406.8	406.1

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	468.2	468.5	468.6	468.8	469.1	469.3	469.5	468.7	467.8	467.0	466.1
115°	528.8	529.3	529.4	529.6	529.9	530.1	530.3	529.5	528.6	527.8	526.9
117.5°	586.4	586.4	586.8	587.7	588.5	589.4	590.2	588.9	587.7	586.4	585.1
120°	642.5	642.4	642.7	643.4	644.0	644.7	645.3	644.9	644.5	644.0	643.6
122.5°	698.0	698.5	698.6	698.8	699.1	699.3	699.5	699.1	698.7	698.2	697.8
125°	752.0	752.7	752.7	752.7	752.7	752.7	752.7	751.9	751.0	750.2	749.3
127.5°	800.6	801.1	801.0	800.8	800.6	800.4	800.2	799.8	799.4	798.9	798.5
130°	846.3	846.8	846.9	847.1	847.3	847.5	847.7	847.1	846.5	845.8	845.2
132.5°	892.7	893.3	893.0	892.4	891.7	891.1	890.5	890.5	890.5	890.5	890.5
135°	935.5	936.1	935.9	935.5	935.0	934.6	934.2	933.8	933.4	932.9	932.5
137.5°	975.4	976.0	975.8	975.4	974.9	974.5	974.1	974.1	974.1	974.1	974.1
140°	1011.0	1011.2	1011.1	1010.9	1010.6	1010.4	1010.2	1010.6	1011.0	1011.5	1011.9
142.5°	1045.3	1045.4	1045.6	1046.0	1046.5	1046.9	1047.3	1047.3	1047.3	1047.3	1047.3
145°	1080.3	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.7	1080.9	1081.2	1081.4
147.5°	1109.1	1109.1	1109.2	1109.4	1109.6	1109.8	1110.0	1110.2	1110.4	1110.7	1110.9
150°	1135.9	1135.7	1135.9	1136.3	1136.8	1137.2	1137.6	1138.0	1138.4	1138.9	1139.3
152.5°	1160.9	1160.4	1160.6	1161.0	1161.5	1161.9	1162.3	1162.7	1163.1	1163.6	1164.0
155°	1182.8	1182.2	1182.4	1182.8	1183.3	1183.7	1184.1	1184.7	1185.4	1186.0	1186.7
157.5°	1203.4	1203.1	1203.1	1203.1	1203.1	1203.1	1203.1	1203.7	1204.4	1205.0	1205.7
160°	1219.9	1219.3	1219.4	1219.6	1219.8	1220.0	1220.2	1221.1	1221.9	1222.8	1223.7
162.5°	1235.1	1234.5	1234.6	1234.8	1235.1	1235.3	1235.5	1236.8	1238.0	1239.3	1240.6
165°	1248.4	1247.8	1247.9	1248.1	1248.4	1248.6	1248.8	1250.1	1251.3	1252.6	1253.9
167.5°	1258.9	1258.3	1258.4	1258.6	1258.8	1259.0	1259.2	1260.7	1262.2	1263.7	1265.2
170°	1266.6	1265.9	1266.0	1266.2	1266.4	1266.6	1266.8	1268.5	1270.2	1271.9	1273.6
172.5°	1272.3	1271.6	1271.8	1272.2	1272.7	1273.1	1273.5	1275.0	1276.4	1277.9	1279.4
175°	1276.9	1276.3	1276.4	1276.6	1276.9	1277.1	1277.3	1279.0	1280.7	1282.4	1284.1
177.5°	1279.8	1279.2	1279.3	1279.5	1279.7	1279.9	1280.1	1281.6	1283.1	1284.6	1286.1
180°	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	483.2	480.2	479.7	480.6	478.9	481.5	480.6	481.5	479.3	481.5	480.2
5°	449.9	449.0	447.3	445.1	445.6	446.0	448.2	446.0	447.7	448.2	450.3
7.5°	418.7	417.0	418.3	417.5	413.6	412.7	413.6	414.9	417.5	419.2	420.5
10°	393.7	392.8	391.1	389.8	387.6	386.3	388.0	386.3	389.8	392.8	392.8
12.5°	374.6	371.2	369.0	368.6	363.8	364.7	366.4	367.7	371.6	373.3	373.3
15°	354.7	352.1	351.3	349.5	347.8	349.5	348.7	350.0	351.7	353.4	354.3
17.5°	337.4	337.0	337.4	333.1	334.4	332.2	332.7	334.8	333.5	334.8	337.4
20°	321.8	322.7	321.4	319.7	319.7	317.1	320.1	319.3	319.7	322.3	326.2
22.5°	310.2	309.7	308.4	307.1	305.4	305.8	306.3	305.4	308.9	311.0	311.5
25°	297.6	296.8	296.3	295.0	293.3	295.0	294.6	295.0	295.9	299.4	296.8
27.5°	285.9	284.2	285.1	283.8	283.3	283.8	283.8	284.2	285.1	285.5	285.9
30°	276.0	274.3	273.8	273.0	272.5	273.0	273.8	273.0	276.4	276.0	276.0
32.5°	265.2	263.9	263.0	263.0	262.6	262.2	262.6	263.0	265.6	263.9	265.6
35°	254.8	253.9	253.9	253.1	252.6	252.6	252.6	254.4	253.5	254.8	254.8
37.5°	244.8	244.8	244.4	243.5	243.1	243.5	243.1	244.0	243.5	244.0	244.4
40°	234.5	233.6	233.2	233.2	231.9	230.6	231.9	231.9	232.3	233.6	234.0
42.5°	221.9	222.4	222.4	220.6	220.6	220.6	221.1	221.5	221.5	222.4	222.4
45°	211.1	210.2	210.2	210.2	209.4	209.8	210.7	210.7	210.7	210.7	209.8
47.5°	199.0	199.0	199.4	199.4	200.7	200.3	200.3	199.9	199.0	199.0	199.4
50°	187.7	189.0	189.5	189.5	189.9	190.3	190.3	189.5	189.0	187.7	187.7
52.5°	176.9	177.8	178.7	180.0	180.8	180.4	180.4	179.5	177.8	177.4	176.9
55°	165.3	166.5	168.3	169.6	170.9	171.3	171.3	169.6	167.8	165.7	165.7
57.5°	154.4	155.7	158.8	160.1	161.8	161.8	160.9	159.6	157.0	155.3	154.0
60°	143.6	145.8	147.9	150.5	152.7	153.1	151.8	150.1	147.1	144.9	143.2
62.5°	131.9	134.1	138.4	141.0	142.8	142.8	142.8	140.6	136.7	133.7	131.1
65°	120.7	122.9	126.7	130.2	131.5	132.8	131.5	129.3	126.3	122.9	120.3
67.5°	109.0	111.6	115.5	118.1	119.8	121.1	120.3	118.5	114.6	109.9	108.1
70°	96.0	97.3	103.0	105.6	108.1	109.0	108.1	105.6	101.7	96.5	94.7
72.5°	83.9	85.2	90.4	92.6	94.7	95.6	94.3	92.6	89.1	84.4	82.2
75°	70.1	72.2	74.8	78.3	80.9	81.8	80.5	79.2	74.8	71.8	70.1
77.5°	55.4	57.5	61.0	64.0	66.6	66.2	64.5	64.9	60.1	56.7	55.4
80°	42.0	43.7	46.3	48.9	50.2	50.2	49.7	48.0	46.3	43.7	41.5
82.5°	29.0	31.1	33.3	35.0	35.0	35.5	34.6	34.2	32.4	30.3	29.8
85°	17.3	17.7	19.5	19.5	21.2	20.3	19.9	21.2	19.5	18.2	17.7
87.5°	7.8	7.4	7.8	7.8	7.4	8.2	8.2	7.8	8.2	7.8	7.8
90°	20.0	20.3	20.9	21.6	22.2	22.8	22.2	21.6	20.9	20.3	20.0
92.5°	20.0	20.1	20.3	20.5	20.7	20.9	20.7	20.5	20.3	20.1	20.0
95°	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0
97.5°	19.0	19.1	19.3	19.6	19.8	20.0	19.8	19.6	19.3	19.1	19.0
100°	23.8	23.4	22.5	21.7	20.8	20.0	20.8	21.7	22.5	23.4	23.8
102.5°	224.3	215.4	197.7	180.0	162.2	144.5	162.2	180.0	197.7	215.4	224.3
105°	283.2	283.1	282.9	282.7	282.5	282.3	282.5	282.7	282.9	283.1	283.2
107.5°	346.9	346.5	345.6	344.8	343.9	343.1	343.9	344.8	345.6	346.5	346.9
110°	405.8	405.9	406.1	406.3	406.5	406.7	406.5	406.3	406.1	405.9	405.8

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	465.7	465.5	465.1	464.6	464.2	463.8	464.2	464.6	465.1	465.5	465.7
115°	526.5	525.9	524.6	523.3	522.1	520.8	522.1	523.3	524.6	525.9	526.5
117.5°	584.5	584.3	583.9	583.4	583.0	582.6	583.0	583.4	583.9	584.3	584.5
120°	643.4	642.9	641.8	640.7	639.7	638.6	639.7	640.7	641.8	642.9	643.4
122.5°	697.6	697.0	695.7	694.4	693.2	691.9	693.2	694.4	695.7	697.0	697.6
125°	748.9	748.6	747.9	747.3	746.6	746.0	746.6	747.3	747.9	748.6	748.9
127.5°	798.3	797.5	795.8	794.1	792.4	790.7	792.4	794.1	795.8	797.5	798.3
130°	844.9	844.4	843.3	842.2	841.2	840.1	841.2	842.2	843.3	844.4	844.9
132.5°	890.5	890.0	888.9	887.8	886.8	885.7	886.8	887.8	888.9	890.0	890.5
135°	932.3	931.7	930.4	929.1	927.9	926.6	927.9	929.1	930.4	931.7	932.3
137.5°	974.1	973.6	972.5	971.5	970.4	969.4	970.4	971.5	972.5	973.6	974.1
140°	1012.1	1011.5	1010.2	1008.9	1007.7	1006.4	1007.7	1008.9	1010.2	1011.5	1012.1
142.5°	1047.3	1046.7	1045.4	1044.1	1042.9	1041.6	1042.9	1044.1	1045.4	1046.7	1047.3
145°	1081.5	1080.9	1079.6	1078.3	1077.1	1075.8	1077.1	1078.3	1079.6	1080.9	1081.5
147.5°	1111.0	1110.3	1108.8	1107.3	1105.8	1104.3	1105.8	1107.3	1108.8	1110.3	1111.0
150°	1139.5	1138.7	1137.0	1135.3	1133.6	1131.9	1133.6	1135.3	1137.0	1138.7	1139.5
152.5°	1164.2	1163.5	1162.0	1160.5	1159.0	1157.5	1159.0	1160.5	1162.0	1163.5	1164.2
155°	1187.0	1186.2	1184.5	1182.8	1181.1	1179.4	1181.1	1182.8	1184.5	1186.2	1187.0
157.5°	1206.0	1205.2	1203.5	1201.8	1200.1	1198.4	1200.1	1201.8	1203.5	1205.2	1206.0
160°	1224.1	1223.2	1221.5	1219.8	1218.1	1216.4	1218.1	1219.8	1221.5	1223.2	1224.1
162.5°	1241.2	1240.2	1238.3	1236.4	1234.5	1232.6	1234.5	1236.4	1238.3	1240.2	1241.2
165°	1254.5	1253.7	1252.0	1250.3	1248.6	1246.9	1248.6	1250.3	1252.0	1253.7	1254.5
167.5°	1265.9	1264.9	1263.0	1261.1	1259.2	1257.3	1259.2	1261.1	1263.0	1264.9	1265.9
170°	1274.4	1273.5	1271.6	1269.7	1267.8	1265.9	1267.8	1269.7	1271.6	1273.5	1274.4
172.5°	1280.1	1279.2	1277.3	1275.4	1273.5	1271.6	1273.5	1275.4	1277.3	1279.2	1280.1
175°	1284.9	1283.9	1282.0	1280.1	1278.2	1276.3	1278.2	1280.1	1282.0	1283.9	1284.9
177.5°	1286.8	1286.0	1284.3	1282.6	1280.9	1279.2	1280.9	1282.6	1284.3	1286.0	1286.8
180°	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	484.1	481.5	484.5	480.6	481.5	486.2	485.8	490.1	492.7	492.3	494.5
5°	452.1	452.1	453.4	452.9	457.3	461.1	466.3	470.7	475.4	478.0	481.0
7.5°	420.5	424.8	425.7	427.8	433.0	439.5	444.7	451.2	458.1	462.9	466.3
10°	394.5	398.0	401.4	403.2	408.8	417.5	424.8	435.2	443.8	449.0	453.8
12.5°	371.6	375.5	377.2	385.0	388.9	394.5	404.9	416.2	425.7	431.3	435.2
15°	355.2	357.3	361.2	366.0	369.9	376.8	385.4	398.0	407.1	411.8	425.2
17.5°	341.3	343.9	346.1	348.2	354.3	361.6	369.9	380.7	392.4	400.6	407.5
20°	327.0	328.3	330.9	334.4	338.7	345.6	353.0	364.2	374.6	381.1	390.2
22.5°	310.2	314.1	316.7	319.3	324.0	331.8	338.7	346.9	359.9	367.3	376.8
25°	300.2	301.9	303.7	306.7	310.2	317.1	324.9	333.5	343.9	351.7	359.9
27.5°	287.2	289.8	292.0	295.9	298.1	303.7	311.0	319.7	332.2	338.7	345.6
30°	276.4	279.0	280.8	282.5	285.5	291.6	298.5	305.4	317.1	325.3	332.2
32.5°	265.6	268.2	270.4	271.7	274.7	278.6	284.2	292.9	302.8	308.4	317.5
35°	256.1	256.1	258.7	260.4	263.0	266.5	271.7	278.2	288.5	295.9	304.1
37.5°	245.3	245.7	247.9	249.2	251.8	255.2	260.4	266.5	275.1	280.8	289.0
40°	234.0	235.3	236.2	238.4	241.4	242.7	247.9	254.8	263.4	268.6	275.6
42.5°	222.8	223.7	225.8	227.5	230.1	232.3	235.8	242.3	248.7	256.5	262.2
45°	210.2	212.4	213.7	216.7	218.0	220.2	223.7	228.8	236.6	241.4	247.9
47.5°	199.4	200.3	201.2	205.0	207.6	208.9	212.4	215.4	223.7	228.0	234.0
50°	187.7	187.7	189.0	190.8	193.8	196.4	199.4	202.9	209.4	213.7	219.8
52.5°	176.9	175.6	176.5	177.4	180.4	183.0	186.0	190.8	196.8	199.4	204.6
55°	165.3	163.1	164.4	165.7	166.5	170.0	173.5	176.5	181.3	185.1	189.9
57.5°	152.7	152.3	151.4	151.8	154.0	156.2	158.8	162.7	168.3	171.3	173.9
60°	141.5	138.9	138.0	138.9	140.2	141.5	144.9	148.4	153.1	156.2	159.2
62.5°	129.8	127.2	125.5	124.2	125.5	128.5	130.6	133.2	137.1	140.6	143.2
65°	118.5	114.6	112.9	112.0	111.6	113.8	115.5	119.0	122.4	123.7	126.7
67.5°	106.0	102.5	100.4	99.1	99.1	99.1	100.8	104.3	107.7	108.1	111.2
70°	93.4	89.5	87.4	85.7	84.8	85.7	87.8	88.2	91.3	92.1	93.9
72.5°	80.0	76.6	74.0	71.8	72.2	73.1	73.1	74.0	75.7	77.9	77.9
75°	67.5	62.7	61.4	59.7	58.8	58.8	58.8	60.6	61.9	63.6	63.2
77.5°	53.2	50.6	48.0	47.2	45.9	45.4	46.3	46.3	47.2	48.5	48.9
80°	41.1	38.1	36.3	35.5	33.7	33.3	33.7	33.7	35.0	34.6	35.0
82.5°	28.6	26.4	25.1	23.8	22.9	23.4	22.9	22.9	23.4	22.9	22.9
85°	16.4	16.0	15.1	14.7	14.3	13.4	14.3	13.8	13.4	13.0	13.8
87.5°	7.8	7.4	7.4	6.5	6.5	6.1	6.5	6.5	6.1	6.1	6.1
90°	19.5	18.4	17.3	16.3	15.2	13.7	12.3	10.8	9.3	8.6	7.8
92.5°	19.5	18.4	17.3	16.3	15.2	13.9	12.7	11.4	10.1	9.5	10.5
95°	19.5	18.4	17.3	16.3	15.2	23.2	31.2	39.3	47.3	51.3	51.6
97.5°	18.8	18.4	17.9	17.5	17.1	37.2	57.2	77.3	97.4	107.4	106.8
100°	39.5	71.0	102.5	133.9	165.4	164.6	163.7	162.9	162.0	161.6	161.3
102.5°	224.1	223.7	223.2	222.8	222.4	222.0	221.6	221.1	220.7	220.5	220.1
105°	283.2	283.2	283.2	283.2	283.2	283.2	283.2	283.2	283.2	283.2	282.8
107.5°	346.8	346.6	346.3	346.1	345.9	345.5	345.1	344.6	344.2	344.0	344.0
110°	406.1	406.8	407.4	408.1	408.7	408.3	407.8	407.4	406.9	406.7	406.7

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	466.1	467.0	467.8	468.7	469.5	469.3	469.1	468.8	468.6	468.5	468.2
115°	526.9	527.8	528.6	529.5	530.3	530.1	529.9	529.6	529.4	529.3	528.8
117.5°	585.1	586.4	587.7	588.9	590.2	589.4	588.5	587.7	586.8	586.4	586.4
120°	643.6	644.0	644.5	644.9	645.3	644.7	644.0	643.4	642.7	642.4	642.5
122.5°	697.8	698.2	698.7	699.1	699.5	699.3	699.1	698.8	698.6	698.5	698.0
125°	749.3	750.2	751.0	751.9	752.7	752.7	752.7	752.7	752.7	752.7	752.0
127.5°	798.5	798.9	799.4	799.8	800.2	800.4	800.6	800.8	801.0	801.1	800.6
130°	845.2	845.8	846.5	847.1	847.7	847.5	847.3	847.1	846.9	846.8	846.3
132.5°	890.5	890.5	890.5	890.5	890.5	891.1	891.7	892.4	893.0	893.3	892.7
135°	932.5	932.9	933.4	933.8	934.2	934.6	935.0	935.5	935.9	936.1	935.5
137.5°	974.1	974.1	974.1	974.1	974.1	974.5	974.9	975.4	975.8	976.0	975.4
140°	1011.9	1011.5	1011.0	1010.6	1010.2	1010.4	1010.6	1010.9	1011.1	1011.2	1011.0
142.5°	1047.3	1047.3	1047.3	1047.3	1047.3	1046.9	1046.5	1046.0	1045.6	1045.4	1045.3
145°	1081.4	1081.2	1080.9	1080.7	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.3
147.5°	1110.9	1110.7	1110.4	1110.2	1110.0	1109.8	1109.6	1109.4	1109.2	1109.1	1109.1
150°	1139.3	1138.9	1138.4	1138.0	1137.6	1137.2	1136.8	1136.3	1135.9	1135.7	1135.9
152.5°	1164.0	1163.6	1163.1	1162.7	1162.3	1161.9	1161.5	1161.0	1160.6	1160.4	1160.9
155°	1186.7	1186.0	1185.4	1184.7	1184.1	1183.7	1183.3	1182.8	1182.4	1182.2	1182.8
157.5°	1205.7	1205.0	1204.4	1203.7	1203.1	1203.1	1203.1	1203.1	1203.1	1203.1	1203.4
160°	1223.7	1222.8	1221.9	1221.1	1220.2	1220.0	1219.8	1219.6	1219.4	1219.3	1219.9
162.5°	1240.6	1239.3	1238.0	1236.8	1235.5	1235.3	1235.1	1234.8	1234.6	1234.5	1235.1
165°	1253.9	1252.6	1251.3	1250.1	1248.8	1248.6	1248.4	1248.1	1247.9	1247.8	1248.4
167.5°	1265.2	1263.7	1262.2	1260.7	1259.2	1259.0	1258.8	1258.6	1258.4	1258.3	1258.9
170°	1273.6	1271.9	1270.2	1268.5	1266.8	1266.6	1266.4	1266.2	1266.0	1265.9	1266.6
172.5°	1279.4	1277.9	1276.4	1275.0	1273.5	1273.1	1272.7	1272.2	1271.8	1271.6	1272.3
175°	1284.1	1282.4	1280.7	1279.0	1277.3	1277.1	1276.9	1276.6	1276.4	1276.3	1276.9
177.5°	1286.1	1284.6	1283.1	1281.6	1280.1	1279.9	1279.7	1279.5	1279.3	1279.2	1279.8
180°	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	509.6	509.6	509.6	509.6
2.5°	497.5	501.8	504.8	510.5
5°	486.2	494.0	501.4	509.2
7.5°	475.0	484.1	495.8	505.7
10°	462.4	474.1	488.0	501.4
12.5°	449.9	463.7	478.9	496.6
15°	434.8	452.5	470.2	489.3
17.5°	421.3	439.5	458.5	482.3
20°	406.2	426.1	446.9	471.1
22.5°	392.8	414.9	436.5	462.0
25°	377.7	399.3	423.1	450.3
27.5°	365.1	385.0	408.4	437.8
30°	350.0	371.6	395.0	424.4
32.5°	335.7	356.5	381.1	410.1
35°	321.0	342.2	364.2	391.9
37.5°	307.1	325.3	347.4	373.8
40°	291.6	311.5	331.4	352.1
42.5°	277.3	295.5	314.1	330.5
45°	261.3	276.9	294.6	308.0
47.5°	246.6	260.4	274.3	284.6
50°	231.9	242.7	253.1	262.2
52.5°	214.6	226.7	232.3	237.9
55°	199.0	205.9	211.1	216.7
57.5°	183.9	186.9	189.5	194.7
60°	164.0	167.4	170.4	174.3
62.5°	146.6	148.4	149.2	153.1
65°	130.2	129.8	131.9	134.1
67.5°	112.5	112.0	114.2	115.1
70°	95.2	94.7	95.2	97.3
72.5°	78.7	78.7	79.2	80.0
75°	63.6	63.6	64.0	64.9
77.5°	48.0	48.9	48.5	50.2
80°	35.0	34.2	35.0	35.9
82.5°	22.9	23.8	23.8	22.9
85°	13.0	13.0	13.0	13.0
87.5°	5.6	5.6	6.1	6.5
90°	6.1	4.4	2.7	1.0
92.5°	12.4	14.3	16.2	18.1
95°	52.3	52.9	53.6	54.2
97.5°	105.5	104.2	103.0	101.7
100°	160.6	160.0	159.3	158.7
102.5°	219.2	218.4	217.5	216.7
105°	281.9	281.1	280.2	279.4
107.5°	344.0	344.0	344.0	344.0
110°	406.7	406.7	406.7	406.7

TEST NUMBER: P1026833

CATALOG NUMBER: S125DIP-B375D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	467.6	466.9	466.3	465.7
115°	527.7	526.7	525.6	524.6
117.5°	586.4	586.4	586.4	586.4
120°	642.7	643.0	643.2	643.4
122.5°	696.9	695.9	694.8	693.8
125°	750.5	749.0	747.5	746.0
127.5°	799.5	798.5	797.4	796.4
130°	845.2	844.1	843.1	842.0
132.5°	891.4	890.1	888.9	887.6
135°	934.2	932.9	931.7	930.4
137.5°	974.1	972.8	971.6	970.3
140°	1010.6	1010.1	1009.7	1009.3
142.5°	1045.1	1044.8	1044.6	1044.4
145°	1079.9	1079.4	1079.0	1078.6
147.5°	1109.1	1109.1	1109.1	1109.1
150°	1136.3	1136.8	1137.2	1137.6
152.5°	1162.0	1163.0	1164.1	1165.1
155°	1184.1	1185.4	1186.6	1187.9
157.5°	1204.1	1204.7	1205.4	1206.0
160°	1221.2	1222.5	1223.7	1225.0
162.5°	1236.4	1237.7	1238.9	1240.2
165°	1249.7	1251.0	1252.2	1253.5
167.5°	1260.2	1261.5	1262.7	1264.0
170°	1268.1	1269.6	1271.0	1272.5
172.5°	1273.8	1275.3	1276.7	1278.2
175°	1278.2	1279.5	1280.7	1282.0
177.5°	1281.1	1282.4	1283.6	1284.9
180°	1282.0	1282.0	1282.0	1282.0

(END OF REPORT)