

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1026893

Luminaire Tested: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1026893
REPORT IS A COMBINATION OF REPORTS P1002072 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4483.0 lumens
Efficiency: N/A
Efficacy: 131.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	40	40	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	34	34	27
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	29	29	23
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	24	24	24	20
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	21	21	17
5	65	54	47	41	59	49	42	37	40	35	31	31	27	25	22	20	18	18	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	22	20	18	16	16	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	18	16	14	14	14	12
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13	13	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	12	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10	10	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3265	3265	3265	3265
5°	3268	3704	3270	2810
10°	3248	4221	3242	2412
15°	3224	4577	3204	2179
20°	3183	5016	3154	1990
25°	3147	5748	3089	1877
30°	3095	6063	3041	1776
35°	3013	4860	2950	1693
40°	2884	3359	2842	1608
45°	2723	2501	2692	1535
50°	2538	2059	2495	1478
55°	2337	1756	2319	1428
60°	2141	1503	2104	1389
65°	1930	1298	1898	1333
70°	1706	1078	1683	1234
75°	1470	834	1449	1072
80°	1160	564	1118	788
85°	743	282	715	401

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 4987 cd/sqm

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	1.1
10°-20°	146.1	3.3
20°-30°	237.3	5.3
30°-40°	290.0	6.5
40°-50°	263.1	5.9
50°-60°	209.5	4.7
60°-70°	145.9	3.3
70°-80°	77.7	1.7
80°-90°	20.7	0.5
90°-100°	33.6	0.8
100°-110°	223.6	5.0
110°-120°	402.7	9.0
120°-130°	516.9	11.5
130°-140°	555.9	12.4
140°-150°	521.7	11.6
150°-160°	422.0	9.4
160°-170°	272.9	6.1
170°-180°	94.1	2.1
0°-30°	432.4	9.6
0°-40°	722.4	16.1
0°-60°	1195.0	26.7
0°-90°	1439.5	32.1
90°-120°	659.9	14.7
90°-150°	2254.4	50.3
90°-180°	3044.0	67.9
0°-180°	4483.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	510	510	510	510	510	
5°	509	588	510	446	509	48
15°	489	734	486	350	489	138
25°	450	903	442	295	450	207
35°	392	725	384	253	392	245
45°	308	342	304	210	308	237
55°	217	211	215	171	217	194
65°	134	129	132	133	134	133
75°	65	64	64	82	65	69
85°	13	14	12	20	13	16
90°	1	18	1	18	1	3
95°	42	15	42	15	42	51
105°	216	218	216	218	216	229
115°	405	402	405	402	405	402
125°	577	577	577	577	577	515
135°	719	716	719	716	719	554
145°	834	831	834	831	834	521
155°	918	912	918	912	918	423
165°	969	964	969	964	969	274
175°	991	986	991	986	991	94
180°	991	991	991	991	991	

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	510.5	513.5	516.9	519.5	523.9	525.2	527.3	528.6	529.9	531.2	532.1
5°	509.2	516.5	523.0	527.8	536.0	539.0	542.9	547.7	553.3	558.0	561.1
7.5°	505.7	517.4	526.0	535.5	546.8	554.2	558.0	568.0	577.1	584.0	593.1
10°	501.4	515.2	528.6	542.9	558.9	567.1	574.9	588.8	601.3	612.6	621.6
12.5°	496.6	513.5	529.5	548.1	569.7	579.7	584.9	608.7	624.2	630.3	648.0
15°	489.3	509.2	532.1	555.0	573.2	584.9	599.1	618.2	633.7	647.2	661.4
17.5°	482.3	504.0	527.3	552.9	579.2	594.4	605.2	622.1	638.9	656.2	669.7
20°	471.1	499.2	523.0	550.3	581.4	592.2	603.5	623.4	641.5	660.1	677.0
22.5°	462.0	488.8	521.3	547.2	573.6	584.4	598.3	619.0	640.7	661.9	686.5
25°	450.3	480.2	508.3	536.0	563.2	574.9	587.5	614.3	636.8	664.0	691.3
27.5°	437.8	468.5	496.6	521.7	547.2	563.2	576.6	604.8	634.6	664.5	699.9
30°	424.4	453.4	480.2	504.8	533.0	549.4	562.8	595.7	629.0	667.1	709.5
32.5°	410.1	437.4	460.3	485.4	515.2	530.4	548.5	584.4	623.8	669.2	722.4
35°	391.9	417.9	438.2	463.7	493.6	513.1	532.1	572.3	618.2	668.8	729.8
37.5°	373.8	394.1	413.6	440.8	475.4	493.2	513.1	557.2	609.5	667.5	732.8
40°	352.1	372.0	388.9	416.6	452.9	473.3	494.0	540.3	599.6	662.7	722.0
42.5°	330.5	347.4	366.0	395.0	430.0	451.6	473.7	525.2	586.6	648.9	692.1
45°	308.0	321.0	341.3	367.7	404.9	425.7	450.8	506.6	568.4	623.8	645.4
47.5°	284.6	297.6	316.7	342.2	379.0	403.6	427.4	483.2	545.5	588.3	588.3
50°	262.2	272.5	291.1	316.7	353.9	376.4	400.6	459.8	510.0	541.6	513.5
52.5°	237.9	249.6	265.2	292.0	328.8	349.1	375.5	426.1	473.7	486.7	443.4
55°	216.7	226.2	241.0	266.5	300.7	321.8	344.3	392.8	433.0	432.2	385.9
57.5°	194.7	202.5	218.0	241.4	273.0	292.0	314.5	356.5	389.3	377.7	334.0
60°	174.3	180.0	195.1	214.1	244.4	262.2	283.8	318.0	343.0	326.6	282.5
62.5°	153.1	159.6	171.7	190.3	217.2	231.4	247.4	282.1	298.1	283.3	238.4
65°	134.1	139.3	150.1	165.7	189.9	202.9	216.7	245.3	260.4	239.2	202.0
67.5°	115.1	121.1	128.9	142.8	161.8	173.9	186.0	210.7	217.6	198.6	167.4
70°	97.3	102.5	109.9	119.8	135.8	146.6	155.7	176.1	180.8	163.1	138.4
72.5°	80.0	83.5	89.5	97.8	112.5	118.5	128.0	141.9	147.9	131.9	114.2
75°	64.9	67.5	71.4	77.4	87.4	93.9	101.7	114.6	114.2	103.0	90.4
77.5°	50.2	50.6	54.9	60.6	66.6	72.2	76.1	85.2	86.1	79.2	68.8
80°	35.9	37.2	38.9	43.3	48.5	50.6	55.4	61.0	61.9	56.7	49.7
82.5°	22.9	23.8	25.1	27.7	31.1	33.7	36.3	38.5	40.7	37.6	32.0
85°	13.0	13.4	14.7	15.6	17.3	18.6	20.8	22.9	22.5	20.3	18.6
87.5°	6.5	6.5	6.5	7.4	8.2	8.2	9.1	9.5	9.9	9.1	8.2
90°	0.7	2.0	3.3	4.6	5.9	6.6	7.2	8.3	9.5	10.6	11.8
92.5°	14.0	12.5	11.0	9.5	8.0	7.3	7.8	8.8	9.8	10.8	11.8
95°	41.9	41.4	40.9	40.4	39.9	39.7	36.6	30.4	24.2	18.0	11.8
97.5°	78.6	79.6	80.6	81.5	82.5	83.0	75.2	59.7	44.2	28.7	13.2
100°	122.7	123.2	123.7	124.2	124.7	124.9	125.2	125.9	126.5	127.2	127.8
102.5°	167.5	168.1	168.8	169.4	170.1	170.4	170.6	170.9	171.2	171.6	171.9
105°	215.9	216.6	217.2	217.9	218.6	218.9	218.9	218.9	218.9	218.9	218.9
107.5°	265.9	265.9	265.9	265.9	265.9	265.9	266.1	266.4	266.7	267.0	267.3
110°	314.4	314.4	314.4	314.4	314.4	314.4	314.6	314.9	315.2	315.5	315.8

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	359.9	360.4	360.9	361.4	361.9	362.1	362.2	362.3	362.5	362.6	362.8
115°	405.4	406.2	407.0	407.9	408.7	409.1	409.2	409.3	409.5	409.6	409.8
117.5°	453.2	453.2	453.2	453.2	453.2	453.2	453.5	454.2	454.8	455.5	456.1
120°	497.2	497.0	496.9	496.7	496.6	496.5	496.7	497.2	497.7	498.2	498.7
122.5°	536.2	537.0	537.8	538.6	539.4	539.8	539.9	540.1	540.2	540.4	540.6
125°	576.6	577.7	578.9	580.0	581.1	581.7	581.7	581.7	581.7	581.7	581.7
127.5°	615.5	616.3	617.1	618.0	618.8	619.2	619.1	618.9	618.8	618.6	618.4
130°	650.7	651.5	652.3	653.2	654.0	654.4	654.5	654.6	654.8	654.9	655.1
132.5°	686.0	687.0	688.0	688.9	689.9	690.4	690.2	689.7	689.2	688.7	688.2
135°	719.0	720.0	721.0	722.0	723.0	723.5	723.3	723.0	722.7	722.3	722.0
137.5°	749.9	750.9	751.9	752.8	753.8	754.3	754.1	753.8	753.5	753.1	752.8
140°	780.0	780.3	780.7	781.0	781.3	781.5	781.4	781.2	781.1	780.9	780.7
142.5°	807.2	807.4	807.5	807.7	807.8	807.9	808.1	808.4	808.7	809.1	809.4
145°	833.6	833.9	834.3	834.6	834.9	835.1	835.1	835.1	835.1	835.1	835.1
147.5°	857.1	857.1	857.1	857.1	857.1	857.1	857.2	857.4	857.5	857.7	857.9
150°	879.2	878.9	878.5	878.2	877.9	877.7	877.9	878.2	878.5	878.9	879.2
152.5°	900.5	899.7	898.9	898.0	897.2	896.8	897.0	897.3	897.6	898.0	898.3
155°	918.1	917.1	916.1	915.2	914.2	913.7	913.9	914.2	914.5	914.9	915.2
157.5°	932.0	931.5	931.0	930.5	930.0	929.8	929.8	929.8	929.8	929.8	929.8
160°	946.7	945.7	944.7	943.8	942.8	942.3	942.4	942.6	942.7	942.9	943.1
162.5°	958.5	957.5	956.5	955.6	954.6	954.1	954.2	954.3	954.5	954.6	954.8
165°	968.8	967.8	966.8	965.9	964.9	964.4	964.5	964.6	964.8	964.9	965.1
167.5°	976.8	975.8	974.8	973.9	972.9	972.4	972.5	972.7	972.8	973.0	973.2
170°	983.5	982.3	981.2	980.0	978.9	978.3	978.4	978.5	978.7	978.8	979.0
172.5°	987.9	986.7	985.6	984.4	983.3	982.7	982.9	983.2	983.5	983.9	984.2
175°	990.8	989.8	988.8	987.9	986.9	986.4	986.5	986.6	986.8	986.9	987.1
177.5°	993.0	992.0	991.0	990.1	989.1	988.6	988.7	988.8	989.0	989.1	989.3
180°	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	533.0	536.0	538.6	540.7	542.5	545.1	543.3	543.8	544.6	546.4	546.4
5°	567.6	572.3	574.9	583.6	585.7	585.3	584.0	590.9	590.5	587.9	587.5
7.5°	601.3	609.5	616.9	623.8	626.0	631.6	632.9	635.9	635.0	639.4	637.2
10°	632.0	645.0	651.9	662.3	664.9	667.5	671.0	672.7	676.6	676.1	676.1
12.5°	655.8	671.4	680.5	683.1	693.0	696.0	699.1	704.7	703.4	703.8	706.4
15°	674.4	689.6	697.3	709.5	716.4	719.8	725.0	731.1	730.2	734.1	733.2
17.5°	688.3	702.5	716.8	735.0	735.4	744.5	756.6	759.2	764.8	760.9	760.9
20°	699.5	718.5	738.9	762.2	764.8	770.4	785.2	795.1	801.6	799.4	800.7
22.5°	711.6	738.9	762.7	786.0	798.6	808.5	822.8	838.4	844.0	847.4	846.6
25°	727.2	755.7	790.8	823.2	836.2	855.2	874.3	889.4	893.7	903.3	894.6
27.5°	743.2	783.4	827.1	865.2	881.6	897.2	920.1	931.4	937.0	941.3	938.3
30°	756.6	812.0	859.6	894.6	906.3	915.4	928.3	930.9	928.8	932.2	936.6
32.5°	777.4	831.4	871.7	888.5	887.2	886.8	876.9	863.0	860.0	851.8	863.0
35°	788.6	831.9	847.4	825.0	815.9	799.4	767.9	747.1	728.9	725.0	725.9
37.5°	782.1	799.0	780.4	721.1	706.4	681.3	639.4	610.0	596.5	586.2	599.6
40°	747.1	728.5	677.4	605.2	584.0	560.2	520.8	504.8	485.8	481.9	499.6
42.5°	689.1	632.5	560.2	504.4	482.3	468.9	436.1	420.9	407.5	401.4	411.4
45°	610.4	541.6	468.9	423.1	404.5	388.5	369.0	353.0	344.3	341.7	350.0
47.5°	529.1	456.4	398.4	364.2	344.8	332.7	314.5	305.4	298.5	299.4	300.7
50°	451.2	385.0	340.5	306.3	296.8	287.2	275.1	267.3	263.9	265.2	264.3
52.5°	384.1	330.5	292.9	266.5	262.2	253.1	243.1	236.6	235.3	235.8	237.1
55°	325.3	283.3	253.5	234.5	229.7	223.2	217.2	212.8	209.4	210.7	210.2
57.5°	280.8	244.0	221.1	205.5	202.0	198.1	192.5	190.3	189.0	186.4	188.6
60°	241.4	211.5	191.6	182.1	179.1	176.5	170.4	167.8	167.0	165.7	169.1
62.5°	204.2	183.0	167.8	159.2	156.2	153.6	150.5	148.4	148.8	147.1	148.8
65°	174.8	157.5	146.6	138.9	135.0	133.2	132.8	129.3	128.9	129.3	129.8
67.5°	147.5	132.8	124.6	119.8	116.8	115.1	113.8	111.6	113.3	112.0	112.9
70°	122.9	112.9	104.3	99.5	98.2	98.6	96.5	95.6	96.0	95.2	96.0
72.5°	99.1	90.8	87.4	83.9	82.2	81.8	80.5	79.2	80.5	80.0	80.0
75°	79.2	73.1	69.2	67.1	67.1	66.2	64.0	64.0	64.0	63.6	64.0
77.5°	61.0	55.8	54.1	51.9	51.9	50.6	50.2	50.2	49.3	50.6	49.7
80°	45.4	41.5	38.9	37.6	37.6	37.2	36.3	35.9	36.3	35.9	35.9
82.5°	29.4	27.7	26.4	25.1	24.7	25.1	24.7	23.8	24.2	23.8	24.7
85°	16.9	15.1	15.1	14.3	14.7	13.8	14.3	13.4	13.0	14.3	13.4
87.5°	7.4	6.9	6.9	6.1	6.1	6.1	5.6	6.1	5.6	5.2	5.6
90°	12.6	13.4	14.2	15.0	15.4	15.6	16.1	16.6	17.1	17.6	17.1
92.5°	12.6	13.4	14.2	15.0	15.4	15.5	15.7	15.8	16.0	16.2	16.0
95°	12.6	13.4	14.2	15.0	15.4	15.4	15.4	15.4	15.4	15.4	15.4
97.5°	13.5	13.9	14.2	14.5	14.7	14.8	14.9	15.1	15.2	15.4	15.2
100°	103.5	79.2	54.9	30.6	18.4	18.1	17.4	16.7	16.1	15.4	16.1
102.5°	172.2	172.5	172.8	173.1	173.3	166.4	152.7	139.0	125.3	111.6	125.3
105°	218.9	218.9	218.9	218.9	218.9	218.8	218.6	218.5	218.3	218.1	218.3
107.5°	267.5	267.7	267.8	268.0	268.1	267.8	267.1	266.4	265.8	265.1	265.8
110°	315.3	314.8	314.3	313.8	313.6	313.7	313.9	314.0	314.2	314.4	314.2

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	362.2	361.5	360.9	360.2	359.9	359.7	359.4	359.1	358.7	358.4	358.7
115°	409.2	408.5	407.9	407.2	406.9	406.4	405.4	404.5	403.5	402.5	403.5
117.5°	455.1	454.1	453.2	452.2	451.7	451.5	451.2	450.9	450.5	450.2	450.5
120°	498.4	498.0	497.7	497.4	497.2	496.8	496.0	495.2	494.4	493.6	494.4
122.5°	540.3	539.9	539.6	539.3	539.1	538.6	537.6	536.7	535.7	534.7	535.7
125°	581.1	580.4	579.8	579.1	578.8	578.6	578.1	577.6	577.1	576.6	577.1
127.5°	618.1	617.8	617.5	617.2	617.0	616.3	615.0	613.7	612.4	611.1	612.4
130°	654.6	654.1	653.6	653.1	652.9	652.5	651.7	650.9	650.1	649.3	650.1
132.5°	688.2	688.2	688.2	688.2	688.2	687.8	687.0	686.1	685.3	684.5	685.3
135°	721.7	721.3	721.0	720.7	720.5	720.0	719.0	718.1	717.1	716.1	717.1
137.5°	752.8	752.8	752.8	752.8	752.8	752.4	751.6	750.8	750.0	749.2	750.0
140°	781.0	781.4	781.7	782.0	782.2	781.7	780.7	779.8	778.8	777.8	778.8
142.5°	809.4	809.4	809.4	809.4	809.4	808.9	807.9	807.0	806.0	805.0	806.0
145°	835.3	835.4	835.6	835.7	835.8	835.3	834.3	833.4	832.4	831.4	832.4
147.5°	858.1	858.2	858.4	858.5	858.6	858.0	856.9	855.8	854.6	853.5	854.6
150°	879.5	879.8	880.1	880.4	880.6	880.0	878.7	877.4	876.1	874.8	876.1
152.5°	898.6	898.9	899.2	899.5	899.7	899.1	898.0	896.9	895.7	894.6	895.7
155°	915.7	916.2	916.7	917.2	917.4	916.7	915.4	914.1	912.8	911.5	912.8
157.5°	930.3	930.8	931.3	931.8	932.0	931.4	930.1	928.8	927.5	926.2	927.5
160°	943.7	944.4	945.0	945.7	946.0	945.3	944.0	942.7	941.4	940.1	941.4
162.5°	955.8	956.8	957.7	958.7	959.2	958.5	957.0	955.5	954.1	952.6	954.1
165°	966.1	967.1	968.0	969.0	969.5	968.8	967.5	966.2	964.9	963.6	964.9
167.5°	974.3	975.5	976.6	977.7	978.3	977.6	976.1	974.6	973.2	971.7	973.2
170°	980.3	981.6	982.9	984.2	984.9	984.2	982.7	981.2	979.8	978.3	979.8
172.5°	985.3	986.5	987.6	988.7	989.3	988.6	987.1	985.6	984.2	982.7	984.2
175°	988.4	989.7	991.0	992.3	993.0	992.3	990.8	989.3	987.9	986.4	987.9
177.5°	990.5	991.6	992.8	993.9	994.5	993.8	992.5	991.2	989.9	988.6	989.9
180°	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	545.5	542.5	543.3	542.5	540.3	539.0	535.5	531.2	529.5	527.3	526.0
5°	589.2	587.0	586.6	583.1	582.3	577.1	568.4	564.1	558.9	553.7	548.5
7.5°	636.8	634.2	625.5	624.2	625.1	618.6	607.4	598.7	587.9	580.5	570.6
10°	676.1	671.0	663.6	664.0	661.0	652.3	641.1	632.0	616.4	606.9	592.7
12.5°	699.9	695.6	694.7	690.4	687.8	676.6	663.2	651.5	639.8	626.8	616.0
15°	728.9	723.3	719.4	713.3	711.6	699.9	685.2	671.8	658.4	646.3	623.4
17.5°	760.9	754.9	740.2	738.9	728.5	717.2	703.0	683.1	668.8	651.5	634.6
20°	797.3	788.6	769.6	764.8	756.6	738.0	718.5	696.5	673.5	655.8	635.9
22.5°	837.9	822.8	808.9	793.8	787.8	764.8	738.0	711.2	683.5	659.3	635.5
25°	890.7	870.8	851.3	836.2	825.8	796.0	760.1	724.6	692.6	661.0	629.9
27.5°	932.2	914.9	893.7	873.8	860.4	825.0	783.9	738.0	698.2	659.7	626.4
30°	935.3	930.1	917.1	906.3	891.6	853.5	808.1	756.2	706.9	660.1	619.5
32.5°	878.6	889.0	894.6	896.3	893.3	871.2	829.7	772.6	714.6	656.2	613.4
35°	756.6	784.3	818.5	831.4	844.0	855.7	834.0	784.3	717.2	655.4	603.9
37.5°	622.9	648.0	704.7	730.6	745.4	791.6	809.4	782.6	722.4	656.2	594.8
40°	502.7	542.5	583.1	618.2	641.1	693.0	748.0	754.0	715.1	648.0	583.1
42.5°	423.1	446.4	477.1	509.6	529.9	591.4	665.8	709.5	692.1	634.6	568.9
45°	360.3	377.7	406.6	417.5	443.4	502.2	581.0	644.1	652.8	613.4	552.4
47.5°	309.3	324.0	342.6	356.0	376.8	420.9	487.5	557.2	598.7	584.4	529.5
50°	272.5	284.6	300.2	308.0	321.4	361.2	411.4	480.6	536.4	541.2	499.6
52.5°	241.8	248.7	260.9	269.5	280.3	304.5	350.0	407.1	469.8	495.8	462.9
55°	215.0	220.6	231.4	237.1	242.7	263.4	298.9	350.8	409.7	443.8	425.2
57.5°	190.8	195.5	204.6	209.8	212.8	232.7	260.0	300.7	353.4	395.0	384.6
60°	170.9	175.2	180.4	184.3	187.7	204.2	223.2	256.1	303.2	343.5	340.9
62.5°	149.7	153.6	159.2	163.1	166.1	176.5	192.5	217.6	257.8	295.0	302.4
65°	131.1	134.1	138.0	139.7	143.6	151.4	164.4	186.9	219.8	253.1	258.3
67.5°	114.2	115.1	117.7	121.6	122.4	129.3	141.0	157.9	183.4	210.7	218.9
70°	96.0	97.3	99.5	102.5	104.3	108.6	118.5	129.8	151.8	175.6	181.7
72.5°	80.0	81.8	82.6	84.4	85.2	92.1	96.5	107.7	122.9	142.8	149.2
75°	64.9	66.6	67.1	67.9	68.8	71.8	77.9	84.8	97.3	110.3	119.0
77.5°	51.5	51.0	51.9	53.2	52.8	55.4	59.3	65.3	73.5	84.4	90.0
80°	36.3	36.3	37.6	38.9	38.5	41.1	42.4	46.7	53.6	60.6	62.7
82.5°	24.2	24.2	25.5	25.5	26.4	26.8	28.6	30.7	36.3	39.8	41.1
85°	13.8	13.8	14.3	14.3	14.3	15.1	16.4	17.3	19.0	21.2	22.1
87.5°	5.6	6.1	6.1	6.1	6.1	6.9	6.9	7.8	8.2	9.1	9.1
90°	16.6	16.1	15.6	15.4	15.0	14.2	13.4	12.6	11.8	10.6	9.5
92.5°	15.8	15.7	15.5	15.4	15.0	14.2	13.4	12.6	11.8	10.8	9.8
95°	15.4	15.4	15.4	15.4	15.0	14.2	13.4	12.6	11.8	18.0	24.2
97.5°	15.1	14.9	14.8	14.7	14.5	14.2	13.9	13.5	13.2	28.7	44.2
100°	16.7	17.4	18.1	18.4	30.6	54.9	79.2	103.5	127.8	127.2	126.5
102.5°	139.0	152.7	166.4	173.3	173.1	172.8	172.5	172.2	171.9	171.6	171.2
105°	218.5	218.6	218.8	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.9
107.5°	266.4	267.1	267.8	268.1	268.0	267.8	267.7	267.5	267.3	267.0	266.7
110°	314.0	313.9	313.7	313.6	313.8	314.3	314.8	315.3	315.8	315.5	315.2

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	359.1	359.4	359.7	359.9	360.2	360.9	361.5	362.2	362.8	362.6	362.5
115°	404.5	405.4	406.4	406.9	407.2	407.9	408.5	409.2	409.8	409.6	409.5
117.5°	450.9	451.2	451.5	451.7	452.2	453.2	454.1	455.1	456.1	455.5	454.8
120°	495.2	496.0	496.8	497.2	497.4	497.7	498.0	498.4	498.7	498.2	497.7
122.5°	536.7	537.6	538.6	539.1	539.3	539.6	539.9	540.3	540.6	540.4	540.2
125°	577.6	578.1	578.6	578.8	579.1	579.8	580.4	581.1	581.7	581.7	581.7
127.5°	613.7	615.0	616.3	617.0	617.2	617.5	617.8	618.1	618.4	618.6	618.8
130°	650.9	651.7	652.5	652.9	653.1	653.6	654.1	654.6	655.1	654.9	654.8
132.5°	686.1	687.0	687.8	688.2	688.2	688.2	688.2	688.2	688.2	688.7	689.2
135°	718.1	719.0	720.0	720.5	720.7	721.0	721.3	721.7	722.0	722.3	722.7
137.5°	750.8	751.6	752.4	752.8	752.8	752.8	752.8	752.8	752.8	753.1	753.5
140°	779.8	780.7	781.7	782.2	782.0	781.7	781.4	781.0	780.7	780.9	781.1
142.5°	807.0	807.9	808.9	809.4	809.4	809.4	809.4	809.4	809.4	809.1	808.7
145°	833.4	834.3	835.3	835.8	835.7	835.6	835.4	835.3	835.1	835.1	835.1
147.5°	855.8	856.9	858.0	858.6	858.5	858.4	858.2	858.1	857.9	857.7	857.5
150°	877.4	878.7	880.0	880.6	880.4	880.1	879.8	879.5	879.2	878.9	878.5
152.5°	896.9	898.0	899.1	899.7	899.5	899.2	898.9	898.6	898.3	898.0	897.6
155°	914.1	915.4	916.7	917.4	917.2	916.7	916.2	915.7	915.2	914.9	914.5
157.5°	928.8	930.1	931.4	932.0	931.8	931.3	930.8	930.3	929.8	929.8	929.8
160°	942.7	944.0	945.3	946.0	945.7	945.0	944.4	943.7	943.1	942.9	942.7
162.5°	955.5	957.0	958.5	959.2	958.7	957.7	956.8	955.8	954.8	954.6	954.5
165°	966.2	967.5	968.8	969.5	969.0	968.0	967.1	966.1	965.1	964.9	964.8
167.5°	974.6	976.1	977.6	978.3	977.7	976.6	975.5	974.3	973.2	973.0	972.8
170°	981.2	982.7	984.2	984.9	984.2	982.9	981.6	980.3	979.0	978.8	978.7
172.5°	985.6	987.1	988.6	989.3	988.7	987.6	986.5	985.3	984.2	983.9	983.5
175°	989.3	990.8	992.3	993.0	992.3	991.0	989.7	988.4	987.1	986.9	986.8
177.5°	991.2	992.5	993.8	994.5	993.9	992.8	991.6	990.5	989.3	989.1	989.0
180°	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	524.3	522.1	519.5	519.5	516.5	515.2	512.6	511.8	509.6	506.1	503.5
5°	542.9	537.3	533.8	530.8	524.3	519.5	514.8	509.6	504.4	498.3	491.4
7.5°	561.1	550.7	545.9	540.7	531.2	521.3	511.8	504.8	497.9	488.4	479.7
10°	580.1	567.1	558.5	551.6	536.8	524.3	510.5	500.5	489.7	477.6	466.3
12.5°	596.1	579.2	571.9	558.9	542.0	526.9	509.6	494.5	480.2	465.9	452.1
15°	609.5	593.5	575.3	570.2	546.8	525.2	505.7	486.2	468.5	454.2	438.2
17.5°	613.8	593.5	584.4	571.9	544.2	521.7	497.0	475.9	459.0	437.8	425.2
20°	615.1	595.7	583.1	571.5	546.8	516.9	492.7	466.8	446.4	425.2	405.3
22.5°	611.7	588.8	576.6	565.4	537.7	512.2	484.1	455.5	431.7	412.3	392.4
25°	605.2	578.4	566.7	554.6	528.2	500.1	469.4	442.1	420.0	396.7	377.2
27.5°	596.5	565.8	552.4	539.9	513.9	487.5	458.5	430.4	405.8	381.1	362.9
30°	585.7	550.3	538.1	521.7	496.6	471.5	445.1	417.0	389.3	366.0	346.1
32.5°	571.9	534.7	518.7	503.1	475.9	452.9	427.8	401.4	374.6	351.7	330.9
35°	559.3	516.9	499.2	483.6	453.4	429.1	408.4	383.7	359.9	336.1	317.5
37.5°	542.5	499.2	478.0	462.0	431.3	406.6	387.2	368.1	343.0	320.1	302.8
40°	524.7	477.1	457.3	441.2	409.2	382.4	363.8	346.9	326.6	305.4	287.2
42.5°	508.7	456.0	434.8	415.3	382.8	359.1	340.0	327.0	308.4	289.4	273.0
45°	488.4	433.5	410.5	390.2	359.1	333.1	314.9	304.5	290.7	272.1	257.8
47.5°	467.6	409.2	385.4	365.5	331.8	308.9	291.1	281.2	271.7	257.0	242.7
50°	440.4	383.7	362.1	339.2	305.8	282.5	267.8	257.8	250.5	240.1	228.0
52.5°	410.5	357.3	334.0	314.1	281.2	260.0	243.1	237.5	230.1	222.4	212.0
55°	379.0	328.8	306.3	286.8	256.5	234.9	221.1	215.0	209.4	203.3	196.4
57.5°	347.4	298.9	277.7	260.4	232.3	211.5	200.3	192.1	188.2	184.7	179.1
60°	308.0	266.9	250.5	234.9	207.2	188.2	177.4	171.3	167.8	166.1	163.5
62.5°	273.4	239.7	221.5	206.3	184.3	167.4	157.0	152.3	149.2	148.4	145.4
65°	236.6	207.6	193.4	180.4	161.4	146.2	137.6	131.9	129.8	129.3	129.3
67.5°	202.0	178.7	164.4	155.3	138.9	125.5	117.2	115.1	113.8	112.0	111.6
70°	169.6	151.0	138.4	130.6	115.9	106.0	99.5	96.0	96.0	94.7	93.9
72.5°	141.0	122.4	114.2	107.7	95.6	87.0	82.2	81.3	78.3	77.9	77.9
75°	110.3	96.5	90.8	85.2	76.1	70.1	66.2	64.0	62.3	62.3	62.7
77.5°	83.1	73.5	68.3	64.0	57.5	53.6	50.6	49.7	48.0	48.0	48.0
80°	58.8	53.6	49.7	46.3	41.5	38.1	36.3	34.6	34.6	34.2	34.6
82.5°	38.1	33.7	31.6	31.1	26.8	25.5	23.4	23.8	22.5	22.1	22.9
85°	22.1	19.9	17.3	16.4	14.7	13.0	12.1	12.5	12.1	11.7	12.1
87.5°	8.7	7.4	6.9	6.9	5.6	5.2	4.8	5.2	4.3	4.3	4.8
90°	8.3	7.2	6.6	5.9	4.6	3.3	2.0	0.7	2.0	3.3	4.6
92.5°	8.8	7.8	7.3	8.0	9.5	11.0	12.5	14.0	12.5	11.0	9.5
95°	30.4	36.6	39.7	39.9	40.4	40.9	41.4	41.9	41.4	40.9	40.4
97.5°	59.7	75.2	83.0	82.5	81.5	80.6	79.6	78.6	79.6	80.6	81.5
100°	125.9	125.2	124.9	124.7	124.2	123.7	123.2	122.7	123.2	123.7	124.2
102.5°	170.9	170.6	170.4	170.1	169.4	168.8	168.1	167.5	168.1	168.8	169.4
105°	218.9	218.9	218.9	218.6	217.9	217.2	216.6	215.9	216.6	217.2	217.9
107.5°	266.4	266.1	265.9	265.9	265.9	265.9	265.9	265.9	265.9	265.9	265.9
110°	314.9	314.6	314.4	314.4	314.4	314.4	314.4	314.4	314.4	314.4	314.4

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	362.3	362.2	362.1	361.9	361.4	360.9	360.4	359.9	360.4	360.9	361.4
115°	409.3	409.2	409.1	408.7	407.9	407.0	406.2	405.4	406.2	407.0	407.9
117.5°	454.2	453.5	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
120°	497.2	496.7	496.5	496.6	496.7	496.9	497.0	497.2	497.0	496.9	496.7
122.5°	540.1	539.9	539.8	539.4	538.6	537.8	537.0	536.2	537.0	537.8	538.6
125°	581.7	581.7	581.7	581.1	580.0	578.9	577.7	576.6	577.7	578.9	580.0
127.5°	618.9	619.1	619.2	618.8	618.0	617.1	616.3	615.5	616.3	617.1	618.0
130°	654.6	654.5	654.4	654.0	653.2	652.3	651.5	650.7	651.5	652.3	653.2
132.5°	689.7	690.2	690.4	689.9	688.9	688.0	687.0	686.0	687.0	688.0	688.9
135°	723.0	723.3	723.5	723.0	722.0	721.0	720.0	719.0	720.0	721.0	722.0
137.5°	753.8	754.1	754.3	753.8	752.8	751.9	750.9	749.9	750.9	751.9	752.8
140°	781.2	781.4	781.5	781.3	781.0	780.7	780.3	780.0	780.3	780.7	781.0
142.5°	808.4	808.1	807.9	807.8	807.7	807.5	807.4	807.2	807.4	807.5	807.7
145°	835.1	835.1	835.1	834.9	834.6	834.3	833.9	833.6	833.9	834.3	834.6
147.5°	857.4	857.2	857.1	857.1	857.1	857.1	857.1	857.1	857.1	857.1	857.1
150°	878.2	877.9	877.7	877.9	878.2	878.5	878.9	879.2	878.9	878.5	878.2
152.5°	897.3	897.0	896.8	897.2	898.0	898.9	899.7	900.5	899.7	898.9	898.0
155°	914.2	913.9	913.7	914.2	915.2	916.1	917.1	918.1	917.1	916.1	915.2
157.5°	929.8	929.8	929.8	930.0	930.5	931.0	931.5	932.0	931.5	931.0	930.5
160°	942.6	942.4	942.3	942.8	943.8	944.7	945.7	946.7	945.7	944.7	943.8
162.5°	954.3	954.2	954.1	954.6	955.6	956.5	957.5	958.5	957.5	956.5	955.6
165°	964.6	964.5	964.4	964.9	965.9	966.8	967.8	968.8	967.8	966.8	965.9
167.5°	972.7	972.5	972.4	972.9	973.9	974.8	975.8	976.8	975.8	974.8	973.9
170°	978.5	978.4	978.3	978.9	980.0	981.2	982.3	983.5	982.3	981.2	980.0
172.5°	983.2	982.9	982.7	983.3	984.4	985.6	986.7	987.9	986.7	985.6	984.4
175°	986.6	986.5	986.4	986.9	987.9	988.8	989.8	990.8	989.8	988.8	987.9
177.5°	988.8	988.7	988.6	989.1	990.1	991.0	992.0	993.0	992.0	991.0	990.1
180°	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	502.7	501.8	499.6	498.3	494.0	488.8	487.1	482.8	484.5	481.5	481.5
5°	489.3	485.4	482.8	478.9	470.7	465.0	459.0	456.0	454.2	452.1	450.3
7.5°	472.0	468.9	466.3	459.0	449.9	442.1	434.8	431.7	426.1	422.2	420.5
10°	456.8	452.5	446.4	437.8	428.3	418.3	411.8	405.3	401.0	398.9	394.1
12.5°	441.2	436.1	429.6	417.0	406.6	400.6	388.9	382.8	380.7	379.0	373.3
15°	425.2	419.6	411.8	400.1	391.1	376.8	369.9	365.1	359.9	359.5	355.2
17.5°	411.0	404.0	397.6	383.3	372.0	359.5	355.6	350.4	345.6	340.5	338.3
20°	392.8	386.3	381.5	366.0	353.4	345.6	339.2	334.8	331.8	326.6	325.7
22.5°	376.4	369.4	362.9	351.3	340.5	330.5	322.7	318.0	316.7	314.5	310.6
25°	360.3	353.4	345.6	334.8	323.6	316.7	309.7	306.7	304.1	300.7	297.6
27.5°	346.9	340.5	333.1	319.7	310.2	305.0	297.6	294.2	290.7	289.0	287.7
30°	330.9	323.6	318.0	307.6	297.2	290.3	285.1	282.1	279.0	277.3	276.4
32.5°	315.4	308.4	304.5	293.3	285.1	276.9	273.0	270.8	269.1	267.3	265.6
35°	302.8	295.9	289.8	279.5	271.2	265.6	262.6	259.1	257.8	256.1	256.1
37.5°	287.2	282.1	276.0	266.0	258.7	254.4	251.8	247.4	247.0	246.1	244.8
40°	273.8	268.6	263.0	254.4	247.9	242.7	239.2	237.1	235.8	234.9	234.0
42.5°	259.6	253.9	251.3	241.4	235.8	230.6	228.8	226.7	226.2	224.5	222.4
45°	245.7	241.0	235.8	228.4	223.7	219.3	216.7	215.0	212.8	212.4	211.1
47.5°	233.6	228.0	223.2	216.3	211.1	207.6	205.5	203.3	201.6	200.3	199.0
50°	218.0	213.7	209.8	202.5	198.1	194.7	191.6	189.9	188.2	188.2	188.2
52.5°	202.9	199.0	195.5	190.3	185.1	182.1	178.7	177.4	176.5	175.2	176.5
55°	188.2	184.3	180.8	176.9	170.9	168.3	164.8	163.5	164.0	164.0	165.3
57.5°	172.6	169.6	167.4	162.7	157.0	154.4	152.3	151.0	151.0	152.7	153.1
60°	157.5	154.4	150.5	146.2	142.8	139.7	138.4	138.9	138.9	139.7	141.9
62.5°	140.6	138.9	136.7	130.6	128.5	126.3	124.6	125.9	125.5	127.6	130.6
65°	125.0	123.3	120.3	117.2	114.6	112.5	112.0	112.5	113.3	115.5	119.0
67.5°	107.7	107.7	105.1	102.5	100.4	98.2	98.6	99.1	99.9	102.5	107.7
70°	93.4	91.7	89.1	87.4	85.7	84.8	83.9	85.7	88.2	90.0	93.9
72.5°	77.9	76.6	74.4	72.7	72.2	71.4	70.9	71.8	74.4	77.4	81.8
75°	61.4	61.9	60.6	59.3	59.3	58.0	58.8	58.8	61.4	64.5	67.9
77.5°	47.6	47.2	46.7	45.9	45.4	45.4	45.4	46.3	48.9	50.6	54.1
80°	33.7	34.2	32.9	33.3	32.9	33.3	33.3	35.0	36.3	38.5	41.1
82.5°	22.5	22.5	21.6	22.1	22.1	22.1	22.5	23.4	25.1	26.8	28.6
85°	12.5	13.0	12.1	13.0	13.0	13.0	13.4	13.8	15.1	15.6	17.3
87.5°	4.8	5.6	5.6	4.8	5.2	5.6	6.1	5.6	6.5	7.4	7.8
90°	5.9	6.6	7.2	8.3	9.5	10.6	11.8	12.6	13.4	14.2	15.0
92.5°	8.0	7.3	7.8	8.8	9.8	10.8	11.8	12.6	13.4	14.2	15.0
95°	39.9	39.7	36.6	30.4	24.2	18.0	11.8	12.6	13.4	14.2	15.0
97.5°	82.5	83.0	75.2	59.7	44.2	28.7	13.2	13.5	13.9	14.2	14.5
100°	124.7	124.9	125.2	125.9	126.5	127.2	127.8	103.5	79.2	54.9	30.6
102.5°	170.1	170.4	170.6	170.9	171.2	171.6	171.9	172.2	172.5	172.8	173.1
105°	218.6	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.9
107.5°	265.9	265.9	266.1	266.4	266.7	267.0	267.3	267.5	267.7	267.8	268.0
110°	314.4	314.4	314.6	314.9	315.2	315.5	315.8	315.3	314.8	314.3	313.8

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	361.9	362.1	362.2	362.3	362.5	362.6	362.8	362.2	361.5	360.9	360.2
115°	408.7	409.1	409.2	409.3	409.5	409.6	409.8	409.2	408.5	407.9	407.2
117.5°	453.2	453.2	453.5	454.2	454.8	455.5	456.1	455.1	454.1	453.2	452.2
120°	496.6	496.5	496.7	497.2	497.7	498.2	498.7	498.4	498.0	497.7	497.4
122.5°	539.4	539.8	539.9	540.1	540.2	540.4	540.6	540.3	539.9	539.6	539.3
125°	581.1	581.7	581.7	581.7	581.7	581.7	581.7	581.1	580.4	579.8	579.1
127.5°	618.8	619.2	619.1	618.9	618.8	618.6	618.4	618.1	617.8	617.5	617.2
130°	654.0	654.4	654.5	654.6	654.8	654.9	655.1	654.6	654.1	653.6	653.1
132.5°	689.9	690.4	690.2	689.7	689.2	688.7	688.2	688.2	688.2	688.2	688.2
135°	723.0	723.5	723.3	723.0	722.7	722.3	722.0	721.7	721.3	721.0	720.7
137.5°	753.8	754.3	754.1	753.8	753.5	753.1	752.8	752.8	752.8	752.8	752.8
140°	781.3	781.5	781.4	781.2	781.1	780.9	780.7	781.0	781.4	781.7	782.0
142.5°	807.8	807.9	808.1	808.4	808.7	809.1	809.4	809.4	809.4	809.4	809.4
145°	834.9	835.1	835.1	835.1	835.1	835.1	835.1	835.3	835.4	835.6	835.7
147.5°	857.1	857.1	857.2	857.4	857.5	857.7	857.9	858.1	858.2	858.4	858.5
150°	877.9	877.7	877.9	878.2	878.5	878.9	879.2	879.5	879.8	880.1	880.4
152.5°	897.2	896.8	897.0	897.3	897.6	898.0	898.3	898.6	898.9	899.2	899.5
155°	914.2	913.7	913.9	914.2	914.5	914.9	915.2	915.7	916.2	916.7	917.2
157.5°	930.0	929.8	929.8	929.8	929.8	929.8	929.8	930.3	930.8	931.3	931.8
160°	942.8	942.3	942.4	942.6	942.7	942.9	943.1	943.7	944.4	945.0	945.7
162.5°	954.6	954.1	954.2	954.3	954.5	954.6	954.8	955.8	956.8	957.7	958.7
165°	964.9	964.4	964.5	964.6	964.8	964.9	965.1	966.1	967.1	968.0	969.0
167.5°	972.9	972.4	972.5	972.7	972.8	973.0	973.2	974.3	975.5	976.6	977.7
170°	978.9	978.3	978.4	978.5	978.7	978.8	979.0	980.3	981.6	982.9	984.2
172.5°	983.3	982.7	982.9	983.2	983.5	983.9	984.2	985.3	986.5	987.6	988.7
175°	986.9	986.4	986.5	986.6	986.8	986.9	987.1	988.4	989.7	991.0	992.3
177.5°	989.1	988.6	988.7	988.8	989.0	989.1	989.3	990.5	991.6	992.8	993.9
180°	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	483.2	480.2	479.7	480.6	478.9	481.5	480.6	481.5	479.3	481.5	480.2
5°	449.9	449.0	447.3	445.1	445.6	446.0	448.2	446.0	447.7	448.2	450.3
7.5°	418.7	417.0	418.3	417.5	413.6	412.7	413.6	414.9	417.5	419.2	420.5
10°	393.7	392.8	391.1	389.8	387.6	386.3	388.0	386.3	389.8	392.8	392.8
12.5°	374.6	371.2	369.0	368.6	363.8	364.7	366.4	367.7	371.6	373.3	373.3
15°	354.7	352.1	351.3	349.5	347.8	349.5	348.7	350.0	351.7	353.4	354.3
17.5°	337.4	337.0	337.4	333.1	334.4	332.2	332.7	334.8	333.5	334.8	337.4
20°	321.8	322.7	321.4	319.7	319.7	317.1	320.1	319.3	319.7	322.3	326.2
22.5°	310.2	309.7	308.4	307.1	305.4	305.8	306.3	305.4	308.9	311.0	311.5
25°	297.6	296.8	296.3	295.0	293.3	295.0	294.6	295.0	295.9	299.4	296.8
27.5°	285.9	284.2	285.1	283.8	283.3	283.8	283.8	284.2	285.1	285.5	285.9
30°	276.0	274.3	273.8	273.0	272.5	273.0	273.8	273.0	276.4	276.0	276.0
32.5°	265.2	263.9	263.0	263.0	262.6	262.2	262.6	263.0	265.6	263.9	265.6
35°	254.8	253.9	253.9	253.1	252.6	252.6	252.6	254.4	253.5	254.8	254.8
37.5°	244.8	244.8	244.4	243.5	243.1	243.5	243.1	244.0	243.5	244.0	244.4
40°	234.5	233.6	233.2	233.2	231.9	230.6	231.9	231.9	232.3	233.6	234.0
42.5°	221.9	222.4	222.4	220.6	220.6	220.6	221.1	221.5	221.5	222.4	222.4
45°	211.1	210.2	210.2	210.2	209.4	209.8	210.7	210.7	210.7	210.7	209.8
47.5°	199.0	199.0	199.4	199.4	200.7	200.3	200.3	199.9	199.0	199.0	199.4
50°	187.7	189.0	189.5	189.5	189.9	190.3	190.3	189.5	189.0	187.7	187.7
52.5°	176.9	177.8	178.7	180.0	180.8	180.4	180.4	179.5	177.8	177.4	176.9
55°	165.3	166.5	168.3	169.6	170.9	171.3	171.3	169.6	167.8	165.7	165.7
57.5°	154.4	155.7	158.8	160.1	161.8	161.8	160.9	159.6	157.0	155.3	154.0
60°	143.6	145.8	147.9	150.5	152.7	153.1	151.8	150.1	147.1	144.9	143.2
62.5°	131.9	134.1	138.4	141.0	142.8	142.8	142.8	140.6	136.7	133.7	131.1
65°	120.7	122.9	126.7	130.2	131.5	132.8	131.5	129.3	126.3	122.9	120.3
67.5°	109.0	111.6	115.5	118.1	119.8	121.1	120.3	118.5	114.6	109.9	108.1
70°	96.0	97.3	103.0	105.6	108.1	109.0	108.1	105.6	101.7	96.5	94.7
72.5°	83.9	85.2	90.4	92.6	94.7	95.6	94.3	92.6	89.1	84.4	82.2
75°	70.1	72.2	74.8	78.3	80.9	81.8	80.5	79.2	74.8	71.8	70.1
77.5°	55.4	57.5	61.0	64.0	66.6	66.2	64.5	64.9	60.1	56.7	55.4
80°	42.0	43.7	46.3	48.9	50.2	50.2	49.7	48.0	46.3	43.7	41.5
82.5°	29.0	31.1	33.3	35.0	35.0	35.5	34.6	34.2	32.4	30.3	29.8
85°	17.3	17.7	19.5	19.5	21.2	20.3	19.9	21.2	19.5	18.2	17.7
87.5°	7.8	7.4	7.8	7.8	7.4	8.2	8.2	7.8	8.2	7.8	7.8
90°	15.4	15.6	16.1	16.6	17.1	17.6	17.1	16.6	16.1	15.6	15.4
92.5°	15.4	15.5	15.7	15.8	16.0	16.2	16.0	15.8	15.7	15.5	15.4
95°	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4
97.5°	14.7	14.8	14.9	15.1	15.2	15.4	15.2	15.1	14.9	14.8	14.7
100°	18.4	18.1	17.4	16.7	16.1	15.4	16.1	16.7	17.4	18.1	18.4
102.5°	173.3	166.4	152.7	139.0	125.3	111.6	125.3	139.0	152.7	166.4	173.3
105°	218.9	218.8	218.6	218.5	218.3	218.1	218.3	218.5	218.6	218.8	218.9
107.5°	268.1	267.8	267.1	266.4	265.8	265.1	265.8	266.4	267.1	267.8	268.1
110°	313.6	313.7	313.9	314.0	314.2	314.4	314.2	314.0	313.9	313.7	313.6

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	359.9	359.7	359.4	359.1	358.7	358.4	358.7	359.1	359.4	359.7	359.9
115°	406.9	406.4	405.4	404.5	403.5	402.5	403.5	404.5	405.4	406.4	406.9
117.5°	451.7	451.5	451.2	450.9	450.5	450.2	450.5	450.9	451.2	451.5	451.7
120°	497.2	496.8	496.0	495.2	494.4	493.6	494.4	495.2	496.0	496.8	497.2
122.5°	539.1	538.6	537.6	536.7	535.7	534.7	535.7	536.7	537.6	538.6	539.1
125°	578.8	578.6	578.1	577.6	577.1	576.6	577.1	577.6	578.1	578.6	578.8
127.5°	617.0	616.3	615.0	613.7	612.4	611.1	612.4	613.7	615.0	616.3	617.0
130°	652.9	652.5	651.7	650.9	650.1	649.3	650.1	650.9	651.7	652.5	652.9
132.5°	688.2	687.8	687.0	686.1	685.3	684.5	685.3	686.1	687.0	687.8	688.2
135°	720.5	720.0	719.0	718.1	717.1	716.1	717.1	718.1	719.0	720.0	720.5
137.5°	752.8	752.4	751.6	750.8	750.0	749.2	750.0	750.8	751.6	752.4	752.8
140°	782.2	781.7	780.7	779.8	778.8	777.8	778.8	779.8	780.7	781.7	782.2
142.5°	809.4	808.9	807.9	807.0	806.0	805.0	806.0	807.0	807.9	808.9	809.4
145°	835.8	835.3	834.3	833.4	832.4	831.4	832.4	833.4	834.3	835.3	835.8
147.5°	858.6	858.0	856.9	855.8	854.6	853.5	854.6	855.8	856.9	858.0	858.6
150°	880.6	880.0	878.7	877.4	876.1	874.8	876.1	877.4	878.7	880.0	880.6
152.5°	899.7	899.1	898.0	896.9	895.7	894.6	895.7	896.9	898.0	899.1	899.7
155°	917.4	916.7	915.4	914.1	912.8	911.5	912.8	914.1	915.4	916.7	917.4
157.5°	932.0	931.4	930.1	928.8	927.5	926.2	927.5	928.8	930.1	931.4	932.0
160°	946.0	945.3	944.0	942.7	941.4	940.1	941.4	942.7	944.0	945.3	946.0
162.5°	959.2	958.5	957.0	955.5	954.1	952.6	954.1	955.5	957.0	958.5	959.2
165°	969.5	968.8	967.5	966.2	964.9	963.6	964.9	966.2	967.5	968.8	969.5
167.5°	978.3	977.6	976.1	974.6	973.2	971.7	973.2	974.6	976.1	977.6	978.3
170°	984.9	984.2	982.7	981.2	979.8	978.3	979.8	981.2	982.7	984.2	984.9
172.5°	989.3	988.6	987.1	985.6	984.2	982.7	984.2	985.6	987.1	988.6	989.3
175°	993.0	992.3	990.8	989.3	987.9	986.4	987.9	989.3	990.8	992.3	993.0
177.5°	994.5	993.8	992.5	991.2	989.9	988.6	989.9	991.2	992.5	993.8	994.5
180°	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	484.1	481.5	484.5	480.6	481.5	486.2	485.8	490.1	492.7	492.3	494.5
5°	452.1	452.1	453.4	452.9	457.3	461.1	466.3	470.7	475.4	478.0	481.0
7.5°	420.5	424.8	425.7	427.8	433.0	439.5	444.7	451.2	458.1	462.9	466.3
10°	394.5	398.0	401.4	403.2	408.8	417.5	424.8	435.2	443.8	449.0	453.8
12.5°	371.6	375.5	377.2	385.0	388.9	394.5	404.9	416.2	425.7	431.3	435.2
15°	355.2	357.3	361.2	366.0	369.9	376.8	385.4	398.0	407.1	411.8	425.2
17.5°	341.3	343.9	346.1	348.2	354.3	361.6	369.9	380.7	392.4	400.6	407.5
20°	327.0	328.3	330.9	334.4	338.7	345.6	353.0	364.2	374.6	381.1	390.2
22.5°	310.2	314.1	316.7	319.3	324.0	331.8	338.7	346.9	359.9	367.3	376.8
25°	300.2	301.9	303.7	306.7	310.2	317.1	324.9	333.5	343.9	351.7	359.9
27.5°	287.2	289.8	292.0	295.9	298.1	303.7	311.0	319.7	332.2	338.7	345.6
30°	276.4	279.0	280.8	282.5	285.5	291.6	298.5	305.4	317.1	325.3	332.2
32.5°	265.6	268.2	270.4	271.7	274.7	278.6	284.2	292.9	302.8	308.4	317.5
35°	256.1	256.1	258.7	260.4	263.0	266.5	271.7	278.2	288.5	295.9	304.1
37.5°	245.3	245.7	247.9	249.2	251.8	255.2	260.4	266.5	275.1	280.8	289.0
40°	234.0	235.3	236.2	238.4	241.4	242.7	247.9	254.8	263.4	268.6	275.6
42.5°	222.8	223.7	225.8	227.5	230.1	232.3	235.8	242.3	248.7	256.5	262.2
45°	210.2	212.4	213.7	216.7	218.0	220.2	223.7	228.8	236.6	241.4	247.9
47.5°	199.4	200.3	201.2	205.0	207.6	208.9	212.4	215.4	223.7	228.0	234.0
50°	187.7	187.7	189.0	190.8	193.8	196.4	199.4	202.9	209.4	213.7	219.8
52.5°	176.9	175.6	176.5	177.4	180.4	183.0	186.0	190.8	196.8	199.4	204.6
55°	165.3	163.1	164.4	165.7	166.5	170.0	173.5	176.5	181.3	185.1	189.9
57.5°	152.7	152.3	151.4	151.8	154.0	156.2	158.8	162.7	168.3	171.3	173.9
60°	141.5	138.9	138.0	138.9	140.2	141.5	144.9	148.4	153.1	156.2	159.2
62.5°	129.8	127.2	125.5	124.2	125.5	128.5	130.6	133.2	137.1	140.6	143.2
65°	118.5	114.6	112.9	112.0	111.6	113.8	115.5	119.0	122.4	123.7	126.7
67.5°	106.0	102.5	100.4	99.1	99.1	99.1	100.8	104.3	107.7	108.1	111.2
70°	93.4	89.5	87.4	85.7	84.8	85.7	87.8	88.2	91.3	92.1	93.9
72.5°	80.0	76.6	74.0	71.8	72.2	73.1	73.1	74.0	75.7	77.9	77.9
75°	67.5	62.7	61.4	59.7	58.8	58.8	58.8	60.6	61.9	63.6	63.2
77.5°	53.2	50.6	48.0	47.2	45.9	45.4	46.3	46.3	47.2	48.5	48.9
80°	41.1	38.1	36.3	35.5	33.7	33.3	33.7	33.7	35.0	34.6	35.0
82.5°	28.6	26.4	25.1	23.8	22.9	23.4	22.9	22.9	23.4	22.9	22.9
85°	16.4	16.0	15.1	14.7	14.3	13.4	14.3	13.8	13.4	13.0	13.8
87.5°	7.8	7.4	7.4	6.5	6.5	6.1	6.5	6.5	6.1	6.1	6.1
90°	15.0	14.2	13.4	12.6	11.8	10.6	9.5	8.3	7.2	6.6	5.9
92.5°	15.0	14.2	13.4	12.6	11.8	10.8	9.8	8.8	7.8	7.3	8.0
95°	15.0	14.2	13.4	12.6	11.8	18.0	24.2	30.4	36.6	39.7	39.9
97.5°	14.5	14.2	13.9	13.5	13.2	28.7	44.2	59.7	75.2	83.0	82.5
100°	30.6	54.9	79.2	103.5	127.8	127.2	126.5	125.9	125.2	124.9	124.7
102.5°	173.1	172.8	172.5	172.2	171.9	171.6	171.2	170.9	170.6	170.4	170.1
105°	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.6
107.5°	268.0	267.8	267.7	267.5	267.3	267.0	266.7	266.4	266.1	265.9	265.9
110°	313.8	314.3	314.8	315.3	315.8	315.5	315.2	314.9	314.6	314.4	314.4

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	360.2	360.9	361.5	362.2	362.8	362.6	362.5	362.3	362.2	362.1	361.9
115°	407.2	407.9	408.5	409.2	409.8	409.6	409.5	409.3	409.2	409.1	408.7
117.5°	452.2	453.2	454.1	455.1	456.1	455.5	454.8	454.2	453.5	453.2	453.2
120°	497.4	497.7	498.0	498.4	498.7	498.2	497.7	497.2	496.7	496.5	496.6
122.5°	539.3	539.6	539.9	540.3	540.6	540.4	540.2	540.1	539.9	539.8	539.4
125°	579.1	579.8	580.4	581.1	581.7	581.7	581.7	581.7	581.7	581.7	581.1
127.5°	617.2	617.5	617.8	618.1	618.4	618.6	618.8	618.9	619.1	619.2	618.8
130°	653.1	653.6	654.1	654.6	655.1	654.9	654.8	654.6	654.5	654.4	654.0
132.5°	688.2	688.2	688.2	688.2	688.2	688.7	689.2	689.7	690.2	690.4	689.9
135°	720.7	721.0	721.3	721.7	722.0	722.3	722.7	723.0	723.3	723.5	723.0
137.5°	752.8	752.8	752.8	752.8	752.8	753.1	753.5	753.8	754.1	754.3	753.8
140°	782.0	781.7	781.4	781.0	780.7	780.9	781.1	781.2	781.4	781.5	781.3
142.5°	809.4	809.4	809.4	809.4	809.4	809.1	808.7	808.4	808.1	807.9	807.8
145°	835.7	835.6	835.4	835.3	835.1	835.1	835.1	835.1	835.1	835.1	834.9
147.5°	858.5	858.4	858.2	858.1	857.9	857.7	857.5	857.4	857.2	857.1	857.1
150°	880.4	880.1	879.8	879.5	879.2	878.9	878.5	878.2	877.9	877.7	877.9
152.5°	899.5	899.2	898.9	898.6	898.3	898.0	897.6	897.3	897.0	896.8	897.2
155°	917.2	916.7	916.2	915.7	915.2	914.9	914.5	914.2	913.9	913.7	914.2
157.5°	931.8	931.3	930.8	930.3	929.8	929.8	929.8	929.8	929.8	929.8	930.0
160°	945.7	945.0	944.4	943.7	943.1	942.9	942.7	942.6	942.4	942.3	942.8
162.5°	958.7	957.7	956.8	955.8	954.8	954.6	954.5	954.3	954.2	954.1	954.6
165°	969.0	968.0	967.1	966.1	965.1	964.9	964.8	964.6	964.5	964.4	964.9
167.5°	977.7	976.6	975.5	974.3	973.2	973.0	972.8	972.7	972.5	972.4	972.9
170°	984.2	982.9	981.6	980.3	979.0	978.8	978.7	978.5	978.4	978.3	978.9
172.5°	988.7	987.6	986.5	985.3	984.2	983.9	983.5	983.2	982.9	982.7	983.3
175°	992.3	991.0	989.7	988.4	987.1	986.9	986.8	986.6	986.5	986.4	986.9
177.5°	993.9	992.8	991.6	990.5	989.3	989.1	989.0	988.8	988.7	988.6	989.1
180°	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	509.6	509.6	509.6	509.6
2.5°	497.5	501.8	504.8	510.5
5°	486.2	494.0	501.4	509.2
7.5°	475.0	484.1	495.8	505.7
10°	462.4	474.1	488.0	501.4
12.5°	449.9	463.7	478.9	496.6
15°	434.8	452.5	470.2	489.3
17.5°	421.3	439.5	458.5	482.3
20°	406.2	426.1	446.9	471.1
22.5°	392.8	414.9	436.5	462.0
25°	377.7	399.3	423.1	450.3
27.5°	365.1	385.0	408.4	437.8
30°	350.0	371.6	395.0	424.4
32.5°	335.7	356.5	381.1	410.1
35°	321.0	342.2	364.2	391.9
37.5°	307.1	325.3	347.4	373.8
40°	291.6	311.5	331.4	352.1
42.5°	277.3	295.5	314.1	330.5
45°	261.3	276.9	294.6	308.0
47.5°	246.6	260.4	274.3	284.6
50°	231.9	242.7	253.1	262.2
52.5°	214.6	226.7	232.3	237.9
55°	199.0	205.9	211.1	216.7
57.5°	183.9	186.9	189.5	194.7
60°	164.0	167.4	170.4	174.3
62.5°	146.6	148.4	149.2	153.1
65°	130.2	129.8	131.9	134.1
67.5°	112.5	112.0	114.2	115.1
70°	95.2	94.7	95.2	97.3
72.5°	78.7	78.7	79.2	80.0
75°	63.6	63.6	64.0	64.9
77.5°	48.0	48.9	48.5	50.2
80°	35.0	34.2	35.0	35.9
82.5°	22.9	23.8	23.8	22.9
85°	13.0	13.0	13.0	13.0
87.5°	5.6	5.6	6.1	6.5
90°	4.6	3.3	2.0	0.7
92.5°	9.5	11.0	12.5	14.0
95°	40.4	40.9	41.4	41.9
97.5°	81.5	80.6	79.6	78.6
100°	124.2	123.7	123.2	122.7
102.5°	169.4	168.8	168.1	167.5
105°	217.9	217.2	216.6	215.9
107.5°	265.9	265.9	265.9	265.9
110°	314.4	314.4	314.4	314.4

TEST NUMBER: P1026893

CATALOG NUMBER: S125DIP-B375D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	361.4	360.9	360.4	359.9
115°	407.9	407.0	406.2	405.4
117.5°	453.2	453.2	453.2	453.2
120°	496.7	496.9	497.0	497.2
122.5°	538.6	537.8	537.0	536.2
125°	580.0	578.9	577.7	576.6
127.5°	618.0	617.1	616.3	615.5
130°	653.2	652.3	651.5	650.7
132.5°	688.9	688.0	687.0	686.0
135°	722.0	721.0	720.0	719.0
137.5°	752.8	751.9	750.9	749.9
140°	781.0	780.7	780.3	780.0
142.5°	807.7	807.5	807.4	807.2
145°	834.6	834.3	833.9	833.6
147.5°	857.1	857.1	857.1	857.1
150°	878.2	878.5	878.9	879.2
152.5°	898.0	898.9	899.7	900.5
155°	915.2	916.1	917.1	918.1
157.5°	930.5	931.0	931.5	932.0
160°	943.8	944.7	945.7	946.7
162.5°	955.6	956.5	957.5	958.5
165°	965.9	966.8	967.8	968.8
167.5°	973.9	974.8	975.8	976.8
170°	980.0	981.2	982.3	983.5
172.5°	984.4	985.6	986.7	987.9
175°	987.9	988.8	989.8	990.8
177.5°	990.1	991.0	992.0	993.0
180°	990.8	990.8	990.8	990.8

(END OF REPORT)